

# Stellaris® LM3S6422 Microcontroller

DATA SHEET

## Copyright

Copyright © 2007-2011 Texas Instruments Incorporated All rights reserved. Stellaris® and StellarisWare® are registered trademarks of Texas Instruments Incorporated. ARM and Thumb are registered trademarks and Cortex is a trademark of ARM Limited. Other names and brands may be claimed as the property of others.

PRODUCTION DATA information is current as of publication date. Products conform to specifications per the terms of Texas Instruments standard warranty. Production processing does not necessarily include testing of all parameters.

A Please be aware that an important notice concerning availability, standard warranty, and use in critical applications of Texas Instruments semiconductor products and disclaimers thereto appears at the end of this data sheet.

Texas Instruments Incorporated 108 Wild Basin, Suite 350 Austin, TX 78746 http://www.ti.com/stellaris http://www-k.ext.ti.com/sc/technical-support/product-information-centers.htm







## **Table of Contents**

<b>Revision His</b>	story	21
About This	Document	26
Audience		26
About This Ma	anual	26
Related Docu	ments	26
Documentatio	n Conventions	27
1	Architectural Overview	29
1.1	Product Features	29
1.2	Target Applications	36
1.3	High-Level Block Diagram	36
1.4	Functional Overview	38
1.4.1	ARM Cortex™-M3	38
1.4.2	Motor Control Peripherals	39
1.4.3	Analog Peripherals	39
1.4.4	Serial Communications Peripherals	40
1.4.5	System Peripherals	41
1.4.6	Memory Peripherals	42
1.4.7	Additional Features	42
1.4.8	Hardware Details	42
2	The Cortex-M3 Processor	44
_ 2.1	Block Diagram	
2.2	Overview	
2.2.1	System-Level Interface	46
2.2.2	Integrated Configurable Debug	46
2.2.3	Trace Port Interface Unit (TPIU)	
2.2.4	Cortex-M3 System Component Details	47
2.3	Programming Model	48
2.3.1	Processor Mode and Privilege Levels for Software Execution	48
2.3.2	Stacks	48
2.3.3	Register Map	49
2.3.4	Register Descriptions	50
2.3.5	Exceptions and Interrupts	63
2.3.6	Data Types	63
2.4	Memory Model	63
2.4.1	Memory Regions, Types and Attributes	64
2.4.2	Memory System Ordering of Memory Accesses	65
2.4.3	Behavior of Memory Accesses	65
2.4.4	Software Ordering of Memory Accesses	66
2.4.5	Bit-Banding	67
2.4.6	Data Storage	69
2.4.7	Synchronization Primitives	70
2.5	Exception Model	71
2.5.1	Exception States	72
2.5.2	Exception Types	72
2.5.3	Exception Handlers	75

2.5.4	Vector Table	75
2.5.5	Exception Priorities	76
2.5.6	Interrupt Priority Grouping	77
2.5.7	Exception Entry and Return	77
2.6	Fault Handling	79
2.6.1	Fault Types	
2.6.2	Fault Escalation and Hard Faults	
2.6.3	Fault Status Registers and Fault Address Registers	81
2.6.4	Lockup	
2.7	Power Management	
2.7.1	Entering Sleep Modes	
2.7.2	Wake Up from Sleep Mode	
2.8	Instruction Set Summary	
3	Cortex-M3 Peripherals	
<b>3</b> .1	Functional Description	
3.1.1	System Timer (SysTick)	
3.1.2	Nested Vectored Interrupt Controller (NVIC)	
3.1.2	System Control Block (SCB)	
3.1.4	Memory Protection Unit (MPU)	
3.1.4	Register Map	
3.3	System Timer (SysTick) Register Descriptions	
3.4	NVIC Register Descriptions	
3.5	System Control Block (SCB) Register Descriptions	
3.6	Memory Protection Unit (MPU) Register Descriptions	
5.0	Memory Frotection Onlit (MFO) Register Descriptions	140
_		
4	JTAG Interface	
4.1	Block Diagram	151
4.1 4.2	Block DiagramSignal Description	151 151
4.1 4.2 4.3	Block Diagram Signal Description Functional Description	151 151 152
4.1 4.2 4.3 4.3.1	Block Diagram Signal Description Functional Description JTAG Interface Pins	151 151 152 152
4.1 4.2 4.3 4.3.1 4.3.2	Block Diagram Signal Description Functional Description  JTAG Interface Pins  JTAG TAP Controller	151 151 152 152 154
4.1 4.2 4.3 4.3.1 4.3.2 4.3.3	Block Diagram Signal Description Functional Description  JTAG Interface Pins  JTAG TAP Controller  Shift Registers	151 151 152 154 155
4.1 4.2 4.3 4.3.1 4.3.2 4.3.3 4.3.4	Block Diagram Signal Description Functional Description  JTAG Interface Pins  JTAG TAP Controller Shift Registers Operational Considerations	151 151 152 154 155
4.1 4.2 4.3 4.3.1 4.3.2 4.3.3 4.3.4 4.4	Block Diagram Signal Description Functional Description  JTAG Interface Pins  JTAG TAP Controller Shift Registers Operational Considerations Initialization and Configuration	151 151 152 154 155 155
4.1 4.2 4.3 4.3.1 4.3.2 4.3.3 4.3.4 4.4	Block Diagram Signal Description Functional Description  JTAG Interface Pins  JTAG TAP Controller Shift Registers Operational Considerations Initialization and Configuration Register Descriptions	151 152 152 154 155 158 158
4.1 4.2 4.3 4.3.1 4.3.2 4.3.3 4.3.4 4.4 4.5 4.5.1	Block Diagram Signal Description Functional Description  JTAG Interface Pins  JTAG TAP Controller Shift Registers Operational Considerations Initialization and Configuration Register Descriptions Instruction Register (IR)	151 151 152 154 155 158 158
4.1 4.2 4.3 4.3.1 4.3.2 4.3.3 4.3.4 4.4	Block Diagram Signal Description Functional Description  JTAG Interface Pins  JTAG TAP Controller Shift Registers Operational Considerations Initialization and Configuration Register Descriptions	151 151 152 154 155 158 158
4.1 4.2 4.3 4.3.1 4.3.2 4.3.3 4.3.4 4.4 4.5 4.5.1	Block Diagram Signal Description Functional Description  JTAG Interface Pins  JTAG TAP Controller Shift Registers Operational Considerations Initialization and Configuration Register Descriptions Instruction Register (IR)	151 152 152 154 155 158 158 158
4.1 4.2 4.3 4.3.1 4.3.2 4.3.3 4.3.4 4.4 4.5 4.5.1 4.5.2	Block Diagram Signal Description Functional Description  JTAG Interface Pins  JTAG TAP Controller Shift Registers Operational Considerations Initialization and Configuration Register Descriptions Instruction Register (IR) Data Registers	151 151 152 154 155 158 158 158 160
4.1 4.2 4.3 4.3.1 4.3.2 4.3.3 4.3.4 4.4 4.5 4.5.1 4.5.2 <b>5</b>	Block Diagram Signal Description Functional Description JTAG Interface Pins JTAG TAP Controller Shift Registers Operational Considerations Initialization and Configuration Register Descriptions Instruction Register (IR) Data Registers  System Control	151 152 152 154 155 158 158 160 163
4.1 4.2 4.3 4.3.1 4.3.2 4.3.3 4.3.4 4.4 4.5 4.5.1 4.5.2 <b>5</b> 5.1	Block Diagram Signal Description Functional Description JTAG Interface Pins JTAG TAP Controller Shift Registers Operational Considerations Initialization and Configuration Register Descriptions Instruction Register (IR) Data Registers  System Control Signal Description	151 152 152 154 155 158 158 160 163 163
4.1 4.2 4.3 4.3.1 4.3.2 4.3.3 4.3.4 4.4 4.5 4.5.1 4.5.2 <b>5</b> 5.1 5.2	Block Diagram Signal Description Functional Description  JTAG Interface Pins  JTAG TAP Controller Shift Registers Operational Considerations Initialization and Configuration Register Descriptions Instruction Register (IR) Data Registers  System Control Signal Description Functional Description	151 152 152 154 155 158 158 160 163 163
4.1 4.2 4.3 4.3.1 4.3.2 4.3.3 4.3.4 4.4 4.5 4.5.1 4.5.2 <b>5</b> 5.1 5.2 5.2.1	Block Diagram Signal Description Functional Description JTAG Interface Pins JTAG TAP Controller Shift Registers Operational Considerations Initialization and Configuration Register Descriptions Instruction Register (IR) Data Registers  System Control Signal Description Functional Description Device Identification	151 152 152 154 155 158 158 160 163 163 164
4.1 4.2 4.3 4.3.1 4.3.2 4.3.3 4.3.4 4.4 4.5 4.5.1 4.5.2 <b>5</b> 5.1 5.2 5.2.1 5.2.2	Block Diagram Signal Description Functional Description JTAG Interface Pins JTAG TAP Controller Shift Registers Operational Considerations Initialization and Configuration Register Descriptions Instruction Register (IR) Data Registers  System Control Signal Description Functional Description Device Identification Reset Control	151 152 152 154 155 158 158 160 163 163 164 164
4.1 4.2 4.3 4.3.1 4.3.2 4.3.3 4.3.4 4.5 4.5.1 4.5.2 <b>5</b> 5.1 5.2 5.2,1 5.2.2 5.2.3	Block Diagram Signal Description Functional Description JTAG Interface Pins JTAG TAP Controller Shift Registers Operational Considerations Initialization and Configuration Register Descriptions Instruction Register (IR) Data Registers  System Control Signal Description Functional Description Device Identification Reset Control Power Control	151 152 152 154 155 158 158 160 163 164 164 168 168
4.1 4.2 4.3 4.3.1 4.3.2 4.3.3 4.3.4 4.5 4.5.1 4.5.2 <b>5</b> 5.1 5.2 5.2,1 5.2,2 5.2,3 5.2,4	Block Diagram Signal Description Functional Description JTAG Interface Pins JTAG TAP Controller Shift Registers Operational Considerations Initialization and Configuration Register Descriptions Instruction Register (IR) Data Registers  System Control Signal Description Functional Description Device Identification Reset Control Power Control Clock Control	151 151 152 154 155 158 158 160 163 163 164 164 169 174
4.1 4.2 4.3 4.3.1 4.3.2 4.3.3 4.3.4 4.4 4.5 4.5.1 4.5.2 <b>5</b> 5.1 5.2 5.2.1 5.2.2 5.2.1 5.2.2 5.2.4 5.2.5	Block Diagram Signal Description Functional Description JTAG Interface Pins JTAG TAP Controller Shift Registers Operational Considerations Initialization and Configuration Register Descriptions Instruction Register (IR) Data Registers  System Control Signal Description Functional Description Device Identification Reset Control Power Control Clock Control System Control System Control	151 152 154 155 158 158 160 163 164 164 164 168 174

6	Internal Memory	225
6.1	Block Diagram	225
6.2	Functional Description	225
6.2.1	SRAM Memory	225
6.2.2	Flash Memory	226
6.3	Flash Memory Initialization and Configuration	227
6.3.1	Flash Programming	227
6.3.2	Nonvolatile Register Programming	228
6.4	Register Map	229
6.5	Flash Register Descriptions (Flash Control Offset)	230
6.6	Flash Register Descriptions (System Control Offset)	238
7	General-Purpose Input/Outputs (GPIOs)	251
7.1	Signal Description	
7.2	Functional Description	255
7.2.1	Data Control	256
7.2.2	Interrupt Control	257
7.2.3	Mode Control	258
7.2.4	Commit Control	258
7.2.5	Pad Control	258
7.2.6	Identification	
7.3	Initialization and Configuration	259
7.4	Register Map	
7.5	Register Descriptions	262
8	General-Purpose Timers	297
8.1	Block Diagram	298
8.2	Signal Description	
8.3	Functional Description	299
8.3.1	GPTM Reset Conditions	
8.3.2	32-Bit Timer Operating Modes	
8.3.3	16-Bit Timer Operating Modes	
8.4	Initialization and Configuration	
8.4.1	32-Bit One-Shot/Periodic Timer Mode	
8.4.2	32-Bit Real-Time Clock (RTC) Mode	
8.4.3	16-Bit One-Shot/Periodic Timer Mode	
8.4.4	16-Bit Input Edge Count Mode	
8.4.5	16-Bit Input Edge Timing Mode	
8.4.6	16-Bit PWM Mode	
8.5	Register Map	
8.6	Register Descriptions	
9	Watchdog Timer	
9.1	Block Diagram	
9.2	Functional Description	
9.3	Initialization and Configuration	
9.4	Register Map	
9.5	Register Descriptions	
10	Analog-to-Digital Converter (ADC)	
10.1	Block Diagram	357

10.2	Signal Description	
10.3	Functional Description	359
10.3.1	Sample Sequencers	359
10.3.2	Module Control	359
10.3.3	Hardware Sample Averaging Circuit	360
10.3.4	Analog-to-Digital Converter	360
	Differential Sampling	
	Test Modes	
10.3.7	Internal Temperature Sensor	
10.4	Initialization and Configuration	
10.4.1	Module Initialization	
10.4.2	Sample Sequencer Configuration	
10.5	Register Map	
10.6	Register Descriptions	
11	Universal Asynchronous Receivers/Transmitters (UARTs)	
11.1	Block Diagram	
11.2	Signal Description	
11.3	Functional Description	
11.3.1	Transmit/Receive Logic	
11.3.1	Baud-Rate Generation	
11.3.2	Data Transmission	
11.3.4	Serial IR (SIR)	
11.3.5	FIFO Operation	
11.3.6 11.3.7	Interrupts	
	Loopback Operation	
11.3.8 11.4	IrDA SIR block	
	Initialization and Configuration	
11.5	Register Map	
11.6	Register Descriptions	
12	Synchronous Serial Interface (SSI)	
12.1	Block Diagram	
12.2	Signal Description	
12.3	Functional Description	
12.3.1	Bit Rate Generation	
	FIFO Operation	
	Interrupts	
	Frame Formats	
12.4	Initialization and Configuration	
12.5	Register Map	
12.6	Register Descriptions	447
13	Ethernet Controller	473
13.1	Block Diagram	473
13.2	Signal Description	474
13.3	Functional Description	476
13.3.1	MAC Operation	476
13.3.2	Internal MII Operation	479
13.3.3	PHY Operation	479
13.3.4	Interrupts	480

13.4	Initialization and Configuration	481
13.4.1	Hardware Configuration	481
13.4.2	Software Configuration	482
13.5	Ethernet Register Map	483
13.6	Ethernet MAC Register Descriptions	484
13.7	MII Management Register Descriptions	502
14	Analog Comparators	521
14.1	Block Diagram	
14.2	Signal Description	
14.3	Functional Description	
14.3.1	Internal Reference Programming	
14.4	Initialization and Configuration	
14.5	Register Map	
14.6	Register Descriptions	
15	Pin Diagram	
16	Signal Tables	
16.1	100-Pin LQFP Package Pin Tables	
16.2	108-Ball BGA Package Pin Tables	
16.3	Connections for Unused Signals	
17	Operating Characteristics	
<b>18</b> 18.1	Electrical Characteristics	
18.1.1	DC Characteristics	
	Maximum Ratings	
	Recommended DC Operating Conditions	
	On-Chip Low Drop-Out (LDO) Regulator Characteristics	
	Power Specifications	
	Ethernet Controller	
18.2		
	AC Characteristics	
	Clocks	
	JTAG and Boundary Scan	
18.2.4	·	
	Sleep Modes	
	General-Purpose I/O (GPIO)	
	Analog-to-Digital Converter	
	Synchronous Serial Interface (SSI)	
	Ethernet Controller	
	Analog Comparator	
Α	Serial Flash Loader	
A.1	Serial Flash Loader	
A.2	Interfaces	
A.2.1	UART	
A.2.2	SSI	
A.3	Packet Handling	
A.3.1	Packet Format	

A.3.2	Sending Packets	576
A.3.3	Receiving Packets	576
A.4	Commands	577
A.4.1	COMMAND_PING (0X20)	577
A.4.2	COMMAND_GET_STATUS (0x23)	577
A.4.3	COMMAND_DOWNLOAD (0x21)	577
A.4.4	COMMAND_SEND_DATA (0x24)	578
A.4.5	COMMAND_RUN (0x22)	578
A.4.6	COMMAND_RESET (0x25)	578
В	Register Quick Reference	580
С	Ordering and Contact Information	599
C.1	Ordering Information	
C.2	Part Markings	599
C.3	Kits	600
C.4	Support Information	600
D	Package Information	601
D.1	100-Pin LQFP Package	
D.1.1	Package Dimensions	601
D.1.2	Tray Dimensions	603
D.1.3	Tape and Reel Dimensions	603
D.2	108-Ball BGA Package	605
D.2.1	Package Dimensions	605
D.2.2	Tray Dimensions	607
D.2.3	-,	

# **List of Figures**

Figure 1-1.	Stellaris LM3S6422 Microcontroller High-Level Block Diagram	37
Figure 2-1.	CPU Block Diagram	46
Figure 2-2.	TPIU Block Diagram	47
Figure 2-3.	Cortex-M3 Register Set	49
Figure 2-4.	Bit-Band Mapping	69
Figure 2-5.	Data Storage	70
Figure 2-6.	Vector Table	76
Figure 2-7.	Exception Stack Frame	78
Figure 3-1.	SRD Use Example	92
Figure 4-1.	JTAG Module Block Diagram	151
Figure 4-2.	Test Access Port State Machine	155
Figure 4-3.	IDCODE Register Format	161
Figure 4-4.	BYPASS Register Format	161
Figure 4-5.	Boundary Scan Register Format	162
Figure 5-1.	Basic RST Configuration	165
Figure 5-2.	External Circuitry to Extend Power-On Reset	166
Figure 5-3.	Reset Circuit Controlled by Switch	166
Figure 5-4.	Power Architecture	169
Figure 5-5.	Main Clock Tree	171
Figure 6-1.	Flash Block Diagram	225
Figure 7-1.	GPIO Port Block Diagram	256
Figure 7-2.	GPIODATA Write Example	257
Figure 7-3.	GPIODATA Read Example	257
Figure 8-1.	GPTM Module Block Diagram	298
Figure 8-2.	16-Bit Input Edge Count Mode Example	302
Figure 8-3.	16-Bit Input Edge Time Mode Example	303
Figure 8-4.	16-Bit PWM Mode Example	304
Figure 9-1.	WDT Module Block Diagram	334
Figure 10-1.	ADC Module Block Diagram	358
Figure 10-2.	Differential Sampling Range, V <sub>IN_ODD</sub> = 1.5 V	362
Figure 10-3.	Differential Sampling Range, V <sub>IN_ODD</sub> = 0.75 V	362
Figure 10-4.	Differential Sampling Range, V <sub>IN ODD</sub> = 2.25 V	
Figure 10-5.	Internal Temperature Sensor Characteristic	
Figure 11-1.	UART Module Block Diagram	
Figure 11-2.	UART Character Frame	395
Figure 11-3.	IrDA Data Modulation	397
Figure 12-1.	SSI Module Block Diagram	435
Figure 12-2.	TI Synchronous Serial Frame Format (Single Transfer)	
Figure 12-3.	TI Synchronous Serial Frame Format (Continuous Transfer)	
Figure 12-4.	Freescale SPI Format (Single Transfer) with SPO=0 and SPH=0	
Figure 12-5.	Freescale SPI Format (Continuous Transfer) with SPO=0 and SPH=0	
Figure 12-6.	Freescale SPI Frame Format with SPO=0 and SPH=1	
Figure 12-7.	Freescale SPI Frame Format (Single Transfer) with SPO=1 and SPH=0	
Figure 12-8.	Freescale SPI Frame Format (Continuous Transfer) with SPO=1 and SPH=0	
Figure 12-9.	Freescale SPI Frame Format with SPO=1 and SPH=1	
•	MICROWIRE Frame Format (Single Frame)	443

Figure 12-11.	MICROWIRE Frame Format (Continuous Transfer)	444
Figure 12-12.	MICROWIRE Frame Format, SSIFss Input Setup and Hold Requirements	445
Figure 13-1.	Ethernet Controller	474
Figure 13-2.	Ethernet Controller Block Diagram	474
Figure 13-3.	Ethernet Frame	476
Figure 13-4.	Interface to an Ethernet Jack	482
Figure 14-1.	Analog Comparator Module Block Diagram	522
Figure 14-2.	Structure of Comparator Unit	523
Figure 14-3.	Comparator Internal Reference Structure	524
Figure 15-1.	100-Pin LQFP Package Pin Diagram	533
Figure 15-2.	108-Ball BGA Package Pin Diagram (Top View)	534
Figure 18-1.	Load Conditions	
Figure 18-2.	JTAG Test Clock Input Timing	566
Figure 18-3.	JTAG Test Access Port (TAP) Timing	566
Figure 18-4.	JTAG TRST Timing	566
Figure 18-5.	External Reset Timing (RST)	567
Figure 18-6.	Power-On Reset Timing	567
Figure 18-7.	Brown-Out Reset Timing	567
Figure 18-8.	Software Reset Timing	568
Figure 18-9.	Watchdog Reset Timing	568
Figure 18-10.	ADC Input Equivalency Diagram	569
Figure 18-11.	SSI Timing for TI Frame Format (FRF=01), Single Transfer Timing	
	Measurement	570
Figure 18-12.	SSI Timing for MICROWIRE Frame Format (FRF=10), Single Transfer	571
Figure 18-13.	SSI Timing for SPI Frame Format (FRF=00), with SPH=1	571
Figure 18-14.	External XTLP Oscillator Characteristics	574
Figure D-1.	Stellaris LM3S6422 100-Pin LQFP Package Dimensions	601
Figure D-2.	100-Pin LQFP Tray Dimensions	603
Figure D-3.	100-Pin LQFP Tape and Reel Dimensions	604
Figure D-4.	Stellaris LM3S6422 108-Ball BGA Package Dimensions	605
Figure D-5.	108-Ball BGA Tray Dimensions	
Figure D-6.	108-Ball BGA Tape and Reel Dimensions	608

## **List of Tables**

Table 1.	Revision History	
Table 2.	Documentation Conventions	27
Table 2-1.	Summary of Processor Mode, Privilege Level, and Stack Use	49
Table 2-2.	Processor Register Map	50
Table 2-3.	PSR Register Combinations	55
Table 2-4.	Memory Map	63
Table 2-5.	Memory Access Behavior	65
Table 2-6.	SRAM Memory Bit-Banding Regions	67
Table 2-7.	Peripheral Memory Bit-Banding Regions	67
Table 2-8.	Exception Types	73
Table 2-9.	Interrupts	74
Table 2-10.	Exception Return Behavior	79
Table 2-11.	Faults	80
Table 2-12.	Fault Status and Fault Address Registers	81
Table 2-13.	Cortex-M3 Instruction Summary	83
Table 3-1.	Core Peripheral Register Regions	86
Table 3-2.	Memory Attributes Summary	89
Table 3-3.	TEX, S, C, and B Bit Field Encoding	92
Table 3-4.	Cache Policy for Memory Attribute Encoding	93
Table 3-5.	AP Bit Field Encoding	93
Table 3-6.	Memory Region Attributes for Stellaris Microcontrollers	93
Table 3-7.	Peripherals Register Map	94
Table 3-8.	Interrupt Priority Levels	119
Table 3-9.	Example SIZE Field Values	147
Table 4-1.	JTAG_SWD_SWO Signals (100LQFP)	151
Table 4-2.	JTAG_SWD_SWO Signals (108BGA)	152
Table 4-3.	JTAG Port Pins Reset State	152
Table 4-4.	JTAG Instruction Register Commands	158
Table 5-1.	System Control & Clocks Signals (100LQFP)	
Table 5-2.	System Control & Clocks Signals (108BGA)	163
Table 5-3.	Reset Sources	164
Table 5-4.	Clock Source Options	
Table 5-5.	Possible System Clock Frequencies Using the SYSDIV Field	
Table 5-6.	Examples of Possible System Clock Frequencies Using the SYSDIV2 Field	
Table 5-7.	System Control Register Map	175
Table 5-8.	RCC2 Fields that Override RCC fields	190
Table 6-1.	Flash Protection Policy Combinations	226
Table 6-2.	User-Programmable Flash Memory Resident Registers	229
Table 6-3.	Flash Register Map	
Table 7-1.	GPIO Pins With Non-Zero Reset Values	252
Table 7-2.	GPIO Pins and Alternate Functions (100LQFP)	252
Table 7-3.	GPIO Pins and Alternate Functions (108BGA)	253
Table 7-4.	GPIO Signals (100LQFP)	254
Table 7-5.	GPIO Signals (108BGA)	
Table 7-6.	GPIO Pad Configuration Examples	259
Table 7-7.	GPIO Interrupt Configuration Example	259

Table 7-8.	GPIO Register Map	261
Table 8-1.	Available CCP Pins	298
Table 8-2.	General-Purpose Timers Signals (100LQFP)	299
Table 8-3.	General-Purpose Timers Signals (108BGA)	299
Table 8-4.	16-Bit Timer With Prescaler Configurations	301
Table 8-5.	Timers Register Map	308
Table 9-1.	Watchdog Timer Register Map	335
Table 10-1.	ADC Signals (100LQFP)	
Table 10-2.	ADC Signals (108BGA)	
Table 10-3.	Samples and FIFO Depth of Sequencers	359
Table 10-4.	Differential Sampling Pairs	361
Table 10-5.	ADC Register Map	365
Table 11-1.	UART Signals (100LQFP)	394
Table 11-2.	UART Signals (108BGA)	395
Table 11-3.	UART Register Map	400
Table 12-1.	SSI Signals (100LQFP)	436
Table 12-2.	SSI Signals (108BGA)	436
Table 12-3.	SSI Register Map	446
Table 13-1.	Ethernet Signals (100LQFP)	475
Table 13-2.	Ethernet Signals (108BGA)	475
Table 13-3.	TX & RX FIFO Organization	478
Table 13-4.	Ethernet Register Map	483
Table 14-1.	Analog Comparators Signals (100LQFP)	522
Table 14-2.	Analog Comparators Signals (108BGA)	523
Table 14-3.	Internal Reference Voltage and ACREFCTL Field Values	524
Table 14-4.	Analog Comparators Register Map	525
Table 16-1.	Signals by Pin Number	535
Table 16-2.	Signals by Signal Name	539
Table 16-3.	Signals by Function, Except for GPIO	542
Table 16-4.	GPIO Pins and Alternate Functions	545
Table 16-5.	Signals by Pin Number	546
Table 16-6.	Signals by Signal Name	550
Table 16-7.	Signals by Function, Except for GPIO	553
Table 16-8.	GPIO Pins and Alternate Functions	556
Table 16-9.	Connections for Unused Signals (100-pin LQFP)	557
Table 16-10.	Connections for Unused Signals, 108-pin BGA	558
Table 17-1.	Temperature Characteristics	559
Table 17-2.	Thermal Characteristics	559
Table 17-3.	ESD Absolute Maximum Ratings	559
Table 18-1.	Maximum Ratings	560
Table 18-2.	Recommended DC Operating Conditions	560
Table 18-3.	LDO Regulator Characteristics	561
Table 18-4.	GPIO Module DC Characteristics	561
Table 18-5.	Detailed Power Specifications	562
Table 18-6.	Flash Memory Characteristics	562
Table 18-7.	Ethernet Controller DC Characteristics	563
Table 18-8.	Phase Locked Loop (PLL) Characteristics	563
Table 18-9.	Actual PLL Frequency	564

Clock Characteristics	564
Crystal Characteristics	564
System Clock Characteristics with ADC Operation	565
JTAG Characteristics	565
Reset Characteristics	566
Sleep Modes AC Characteristics	568
GPIO Characteristics	568
ADC Characteristics	569
ADC Module Internal Reference Characteristics	570
SSI Characteristics	570
100BASE-TX Transmitter Characteristics	571
100BASE-TX Transmitter Characteristics (informative)	572
100BASE-TX Receiver Characteristics	572
10BASE-T Transmitter Characteristics	572
10BASE-T Transmitter Characteristics (informative)	572
10BASE-T Receiver Characteristics	573
Isolation Transformers	573
Ethernet Reference Crystal	573
External XTLP Oscillator Characteristics	574
Analog Comparator Characteristics	574
Analog Comparator Voltage Reference Characteristics	574
Part Ordering Information	599
	Crystal Characteristics System Clock Characteristics with ADC Operation JTAG Characteristics Reset Characteristics Sleep Modes AC Characteristics GPIO Characteristics ADC Characteristics ADC Module Internal Reference Characteristics SSI Characteristics 100BASE-TX Transmitter Characteristics (informative) 100BASE-TX Receiver Characteristics 10BASE-T Transmitter Characteristics (informative) 10BASE-T Receiver Characteristics (informative) 10BASE-T Receiver Characteristics 10BASE-T Receiver Characteris

# **List of Registers**

The Cortex.	-M3 Processor	44
Register 1:	Cortex General-Purpose Register 0 (R0)	
Register 2:	Cortex General-Purpose Register 1 (R1)	51
Register 3:	Cortex General-Purpose Register 2 (R2)	51
Register 4:	Cortex General-Purpose Register 3 (R3)	51
Register 5:	Cortex General-Purpose Register 4 (R4)	51
Register 6:	Cortex General-Purpose Register 5 (R5)	51
Register 7:	Cortex General-Purpose Register 6 (R6)	51
Register 8:	Cortex General-Purpose Register 7 (R7)	51
Register 9:	Cortex General-Purpose Register 8 (R8)	51
Register 10:	Cortex General-Purpose Register 9 (R9)	51
Register 11:	Cortex General-Purpose Register 10 (R10)	51
Register 12:	Cortex General-Purpose Register 11 (R11)	51
Register 13:	Cortex General-Purpose Register 12 (R12)	
Register 14:	Stack Pointer (SP)	52
Register 15:	Link Register (LR)	
Register 16:	Program Counter (PC)	
Register 17:	Program Status Register (PSR)	55
Register 18:	Priority Mask Register (PRIMASK)	
Register 19:	Fault Mask Register (FAULTMASK)	
Register 20:	Base Priority Mask Register (BASEPRI)	
Register 21:	Control Register (CONTROL)	62
Cortex-M3 I	Peripherals	
Register 1:	SysTick Control and Status Register (STCTRL), offset 0x010	
Register 2:	SysTick Reload Value Register (STRELOAD), offset 0x014	
Dogiotor 2:		400
Register 3:	SysTick Current Value Register (STCURRENT), offset 0x018	
Register 4:	Interrupt 0-31 Set Enable (EN0), offset 0x100	101
Register 4: Register 5:	Interrupt 0-31 Set Enable (EN0), offset 0x100	101 102
Register 4: Register 5: Register 6:	Interrupt 0-31 Set Enable (EN0), offset 0x100 Interrupt 32-43 Set Enable (EN1), offset 0x104 Interrupt 0-31 Clear Enable (DIS0), offset 0x180	101 102 103
Register 4: Register 5: Register 6: Register 7:	Interrupt 0-31 Set Enable (EN0), offset 0x100 Interrupt 32-43 Set Enable (EN1), offset 0x104 Interrupt 0-31 Clear Enable (DIS0), offset 0x180 Interrupt 32-43 Clear Enable (DIS1), offset 0x184	101 102 103 104
Register 4: Register 5: Register 6: Register 7: Register 8:	Interrupt 0-31 Set Enable (EN0), offset 0x100 Interrupt 32-43 Set Enable (EN1), offset 0x104 Interrupt 0-31 Clear Enable (DIS0), offset 0x180 Interrupt 32-43 Clear Enable (DIS1), offset 0x184 Interrupt 0-31 Set Pending (PEND0), offset 0x200	101 102 103 104 105
Register 4: Register 5: Register 6: Register 7: Register 8: Register 9:	Interrupt 0-31 Set Enable (EN0), offset 0x100 Interrupt 32-43 Set Enable (EN1), offset 0x104 Interrupt 0-31 Clear Enable (DIS0), offset 0x180 Interrupt 32-43 Clear Enable (DIS1), offset 0x184 Interrupt 0-31 Set Pending (PEND0), offset 0x200 Interrupt 32-43 Set Pending (PEND1), offset 0x204	101 102 103 104 105 106
Register 4: Register 5: Register 6: Register 7: Register 8: Register 9: Register 10:	Interrupt 0-31 Set Enable (EN0), offset 0x100 Interrupt 32-43 Set Enable (EN1), offset 0x104 Interrupt 0-31 Clear Enable (DIS0), offset 0x180 Interrupt 32-43 Clear Enable (DIS1), offset 0x184 Interrupt 0-31 Set Pending (PEND0), offset 0x200 Interrupt 32-43 Set Pending (PEND1), offset 0x204 Interrupt 0-31 Clear Pending (UNPEND0), offset 0x280	101 102 103 104 105 106 107
Register 4: Register 5: Register 6: Register 7: Register 8: Register 9: Register 10: Register 11:	Interrupt 0-31 Set Enable (EN0), offset 0x100 Interrupt 32-43 Set Enable (EN1), offset 0x104 Interrupt 0-31 Clear Enable (DIS0), offset 0x180 Interrupt 32-43 Clear Enable (DIS1), offset 0x184 Interrupt 0-31 Set Pending (PEND0), offset 0x200 Interrupt 32-43 Set Pending (PEND1), offset 0x204 Interrupt 0-31 Clear Pending (UNPEND0), offset 0x280 Interrupt 32-43 Clear Pending (UNPEND1), offset 0x284	101 102 103 104 105 106 107 108
Register 4: Register 5: Register 6: Register 7: Register 8: Register 9: Register 10: Register 11: Register 12:	Interrupt 0-31 Set Enable (EN0), offset 0x100 Interrupt 32-43 Set Enable (EN1), offset 0x104 Interrupt 0-31 Clear Enable (DIS0), offset 0x180 Interrupt 32-43 Clear Enable (DIS1), offset 0x184 Interrupt 0-31 Set Pending (PEND0), offset 0x200 Interrupt 32-43 Set Pending (PEND1), offset 0x204 Interrupt 0-31 Clear Pending (UNPEND0), offset 0x280 Interrupt 32-43 Clear Pending (UNPEND1), offset 0x284 Interrupt 0-31 Active Bit (ACTIVE0), offset 0x300	101 102 103 104 105 106 107 108 109
Register 4: Register 5: Register 6: Register 7: Register 8: Register 9: Register 10: Register 11: Register 12: Register 13:	Interrupt 0-31 Set Enable (EN0), offset 0x100 Interrupt 32-43 Set Enable (EN1), offset 0x104 Interrupt 0-31 Clear Enable (DIS0), offset 0x180 Interrupt 32-43 Clear Enable (DIS1), offset 0x184 Interrupt 0-31 Set Pending (PEND0), offset 0x200 Interrupt 32-43 Set Pending (PEND1), offset 0x204 Interrupt 0-31 Clear Pending (UNPEND0), offset 0x280 Interrupt 32-43 Clear Pending (UNPEND1), offset 0x284 Interrupt 0-31 Active Bit (ACTIVE0), offset 0x300 Interrupt 32-43 Active Bit (ACTIVE1), offset 0x304	101 102 103 104 105 106 107 108 109
Register 4: Register 5: Register 6: Register 7: Register 8: Register 9: Register 10: Register 11: Register 12: Register 13: Register 14:	Interrupt 0-31 Set Enable (EN0), offset 0x100 Interrupt 32-43 Set Enable (EN1), offset 0x104 Interrupt 0-31 Clear Enable (DIS0), offset 0x180 Interrupt 32-43 Clear Enable (DIS1), offset 0x184 Interrupt 0-31 Set Pending (PEND0), offset 0x200 Interrupt 32-43 Set Pending (PEND1), offset 0x204 Interrupt 0-31 Clear Pending (UNPEND0), offset 0x280 Interrupt 32-43 Clear Pending (UNPEND1), offset 0x284 Interrupt 0-31 Active Bit (ACTIVE0), offset 0x300 Interrupt 32-43 Active Bit (ACTIVE1), offset 0x304 Interrupt 0-3 Priority (PRI0), offset 0x400	101 102 103 104 105 106 107 108 109 110
Register 4: Register 5: Register 6: Register 7: Register 8: Register 9: Register 10: Register 11: Register 12: Register 13: Register 14: Register 15:	Interrupt 0-31 Set Enable (EN0), offset 0x100 Interrupt 32-43 Set Enable (EN1), offset 0x104 Interrupt 0-31 Clear Enable (DIS0), offset 0x180 Interrupt 32-43 Clear Enable (DIS1), offset 0x184 Interrupt 0-31 Set Pending (PEND0), offset 0x200 Interrupt 32-43 Set Pending (PEND1), offset 0x204 Interrupt 0-31 Clear Pending (UNPEND0), offset 0x280 Interrupt 32-43 Clear Pending (UNPEND1), offset 0x284 Interrupt 0-31 Active Bit (ACTIVE0), offset 0x300 Interrupt 32-43 Active Bit (ACTIVE1), offset 0x304 Interrupt 0-3 Priority (PRI0), offset 0x400 Interrupt 4-7 Priority (PRI1), offset 0x404	101 102 103 104 105 106 107 108 109 110 111
Register 4: Register 5: Register 6: Register 7: Register 8: Register 9: Register 10: Register 11: Register 12: Register 13: Register 14: Register 15: Register 16:	Interrupt 0-31 Set Enable (EN0), offset 0x100 Interrupt 32-43 Set Enable (EN1), offset 0x104 Interrupt 0-31 Clear Enable (DIS0), offset 0x180 Interrupt 32-43 Clear Enable (DIS1), offset 0x184 Interrupt 0-31 Set Pending (PEND0), offset 0x200 Interrupt 32-43 Set Pending (PEND1), offset 0x204 Interrupt 0-31 Clear Pending (UNPEND0), offset 0x280 Interrupt 32-43 Clear Pending (UNPEND1), offset 0x284 Interrupt 0-31 Active Bit (ACTIVE0), offset 0x300 Interrupt 32-43 Active Bit (ACTIVE1), offset 0x304 Interrupt 0-3 Priority (PRI0), offset 0x400 Interrupt 4-7 Priority (PRI1), offset 0x404 Interrupt 8-11 Priority (PRI2), offset 0x408	101 102 103 104 105 106 107 108 109 110 111 111
Register 4: Register 5: Register 6: Register 7: Register 8: Register 9: Register 10: Register 11: Register 12: Register 13: Register 14: Register 15: Register 16: Register 17:	Interrupt 0-31 Set Enable (EN0), offset 0x100 Interrupt 32-43 Set Enable (EN1), offset 0x104 Interrupt 0-31 Clear Enable (DIS0), offset 0x180 Interrupt 32-43 Clear Enable (DIS1), offset 0x184 Interrupt 0-31 Set Pending (PEND0), offset 0x200 Interrupt 32-43 Set Pending (PEND1), offset 0x204 Interrupt 0-31 Clear Pending (UNPEND0), offset 0x280 Interrupt 32-43 Clear Pending (UNPEND1), offset 0x284 Interrupt 0-31 Active Bit (ACTIVE0), offset 0x300 Interrupt 32-43 Active Bit (ACTIVE1), offset 0x304 Interrupt 0-3 Priority (PRI0), offset 0x400 Interrupt 4-7 Priority (PRI1), offset 0x404 Interrupt 8-11 Priority (PRI2), offset 0x408 Interrupt 12-15 Priority (PRI3), offset 0x40C	101 102 103 104 105 106 107 108 109 110 111 111 111
Register 4: Register 5: Register 6: Register 7: Register 8: Register 9: Register 10: Register 11: Register 12: Register 13: Register 14: Register 15: Register 16: Register 17: Register 17:	Interrupt 0-31 Set Enable (EN0), offset 0x100 Interrupt 32-43 Set Enable (EN1), offset 0x104 Interrupt 0-31 Clear Enable (DIS0), offset 0x180 Interrupt 32-43 Clear Enable (DIS1), offset 0x200 Interrupt 0-31 Set Pending (PEND0), offset 0x200 Interrupt 32-43 Set Pending (PEND1), offset 0x204 Interrupt 0-31 Clear Pending (UNPEND0), offset 0x280 Interrupt 32-43 Clear Pending (UNPEND1), offset 0x284 Interrupt 0-31 Active Bit (ACTIVE0), offset 0x300 Interrupt 32-43 Active Bit (ACTIVE1), offset 0x304 Interrupt 0-3 Priority (PRI0), offset 0x400 Interrupt 4-7 Priority (PRI1), offset 0x404 Interrupt 8-11 Priority (PRI2), offset 0x408 Interrupt 12-15 Priority (PRI3), offset 0x40C Interrupt 16-19 Priority (PRI4), offset 0x410	101 102 103 104 105 106 107 108 109 110 111 111 111 111
Register 4: Register 5: Register 6: Register 7: Register 8: Register 9: Register 10: Register 11: Register 12: Register 14: Register 14: Register 15: Register 16: Register 17: Register 17: Register 17: Register 18: Register 19:	Interrupt 0-31 Set Enable (EN0), offset 0x100 Interrupt 32-43 Set Enable (EN1), offset 0x104 Interrupt 0-31 Clear Enable (DIS0), offset 0x180 Interrupt 32-43 Clear Enable (DIS1), offset 0x284 Interrupt 0-31 Set Pending (PEND0), offset 0x200 Interrupt 32-43 Set Pending (PEND1), offset 0x204 Interrupt 0-31 Clear Pending (UNPEND0), offset 0x280 Interrupt 32-43 Clear Pending (UNPEND1), offset 0x284 Interrupt 0-31 Active Bit (ACTIVE0), offset 0x300 Interrupt 32-43 Active Bit (ACTIVE1), offset 0x304 Interrupt 0-3 Priority (PRI0), offset 0x400 Interrupt 4-7 Priority (PRI1), offset 0x404 Interrupt 8-11 Priority (PRI2), offset 0x408 Interrupt 12-15 Priority (PRI3), offset 0x40C Interrupt 16-19 Priority (PRI4), offset 0x411 Interrupt 20-23 Priority (PRI5), offset 0x414	101 102 103 104 105 106 107 108 109 110 111 111 111 111 111
Register 4: Register 5: Register 6: Register 7: Register 8: Register 9: Register 10: Register 11: Register 12: Register 13: Register 14: Register 15: Register 16: Register 17: Register 17: Register 18: Register 19: Register 20:	Interrupt 0-31 Set Enable (EN0), offset 0x100 Interrupt 32-43 Set Enable (EN1), offset 0x104 Interrupt 0-31 Clear Enable (DIS0), offset 0x180 Interrupt 32-43 Clear Enable (DIS1), offset 0x204 Interrupt 0-31 Set Pending (PEND0), offset 0x200 Interrupt 32-43 Set Pending (PEND1), offset 0x204 Interrupt 0-31 Clear Pending (UNPEND0), offset 0x280 Interrupt 32-43 Clear Pending (UNPEND1), offset 0x284 Interrupt 0-31 Active Bit (ACTIVE0), offset 0x300 Interrupt 32-43 Active Bit (ACTIVE1), offset 0x304 Interrupt 0-3 Priority (PRI0), offset 0x400 Interrupt 4-7 Priority (PRI1), offset 0x404 Interrupt 8-11 Priority (PRI2), offset 0x408 Interrupt 12-15 Priority (PRI3), offset 0x406 Interrupt 16-19 Priority (PRI4), offset 0x410 Interrupt 20-23 Priority (PRI5), offset 0x414 Interrupt 24-27 Priority (PRI6), offset 0x418	101 102 103 104 105 106 107 108 109 110 111 111 111 111 111 111
Register 4: Register 5: Register 6: Register 7: Register 8: Register 9: Register 10: Register 11: Register 12: Register 14: Register 14: Register 15: Register 16: Register 17: Register 17: Register 17: Register 18: Register 19:	Interrupt 0-31 Set Enable (EN0), offset 0x100 Interrupt 32-43 Set Enable (EN1), offset 0x104 Interrupt 0-31 Clear Enable (DIS0), offset 0x180 Interrupt 32-43 Clear Enable (DIS1), offset 0x284 Interrupt 0-31 Set Pending (PEND0), offset 0x200 Interrupt 32-43 Set Pending (PEND1), offset 0x204 Interrupt 0-31 Clear Pending (UNPEND0), offset 0x280 Interrupt 32-43 Clear Pending (UNPEND1), offset 0x284 Interrupt 0-31 Active Bit (ACTIVE0), offset 0x300 Interrupt 32-43 Active Bit (ACTIVE1), offset 0x304 Interrupt 0-3 Priority (PRI0), offset 0x400 Interrupt 4-7 Priority (PRI1), offset 0x404 Interrupt 8-11 Priority (PRI2), offset 0x408 Interrupt 12-15 Priority (PRI3), offset 0x40C Interrupt 16-19 Priority (PRI4), offset 0x411 Interrupt 20-23 Priority (PRI5), offset 0x414	101 102 103 104 105 106 107 108 109 110 111 111 111 111 111 111 111

Register 23:	Interrupt 36-39 Priority (PRI9), offset 0x424	111
Register 24:	Interrupt 40-43 Priority (PRI10), offset 0x428	111
Register 25:	Software Trigger Interrupt (SWTRIG), offset 0xF00	113
Register 26:	CPU ID Base (CPUID), offset 0xD00	114
Register 27:	Interrupt Control and State (INTCTRL), offset 0xD04	115
Register 28:	Vector Table Offset (VTABLE), offset 0xD08	118
Register 29:	Application Interrupt and Reset Control (APINT), offset 0xD0C	119
Register 30:	System Control (SYSCTRL), offset 0xD10	121
Register 31:	Configuration and Control (CFGCTRL), offset 0xD14	123
Register 32:	System Handler Priority 1 (SYSPRI1), offset 0xD18	
Register 33:	System Handler Priority 2 (SYSPRI2), offset 0xD1C	126
Register 34:	System Handler Priority 3 (SYSPRI3), offset 0xD20	127
Register 35:	System Handler Control and State (SYSHNDCTRL), offset 0xD24	128
Register 36:	Configurable Fault Status (FAULTSTAT), offset 0xD28	
Register 37:	Hard Fault Status (HFAULTSTAT), offset 0xD2C	138
Register 38:	Memory Management Fault Address (MMADDR), offset 0xD34	139
Register 39:	Bus Fault Address (FAULTADDR), offset 0xD38	140
Register 40:	MPU Type (MPUTYPE), offset 0xD90	141
Register 41:	MPU Control (MPUCTRL), offset 0xD94	142
Register 42:	MPU Region Number (MPUNUMBER), offset 0xD98	144
Register 43:	MPU Region Base Address (MPUBASE), offset 0xD9C	145
Register 44:	MPU Region Base Address Alias 1 (MPUBASE1), offset 0xDA4	145
Register 45:	MPU Region Base Address Alias 2 (MPUBASE2), offset 0xDAC	
Register 46:	MPU Region Base Address Alias 3 (MPUBASE3), offset 0xDB4	145
Register 47:	MPU Region Attribute and Size (MPUATTR), offset 0xDA0	147
Register 48:	MPU Region Attribute and Size Alias 1 (MPUATTR1), offset 0xDA8	147
Register 49:	MPU Region Attribute and Size Alias 2 (MPUATTR2), offset 0xDB0	147
Register 50:	MPU Region Attribute and Size Alias 3 (MPUATTR3), offset 0xDB8	147
System Co	ntrol	163
Register 1:	Device Identification 0 (DID0), offset 0x000	
Register 2:	Brown-Out Reset Control (PBORCTL), offset 0x030	179
Register 3:	LDO Power Control (LDOPCTL), offset 0x034	180
Register 4:	Raw Interrupt Status (RIS), offset 0x050	181
Register 5:	Interrupt Mask Control (IMC), offset 0x054	182
Register 6:	Masked Interrupt Status and Clear (MISC), offset 0x058	183
Register 7:	Reset Cause (RESC), offset 0x05C	
Register 8:	Run-Mode Clock Configuration (RCC), offset 0x060	185
Register 9:	XTAL to PLL Translation (PLLCFG), offset 0x064	189
Register 10:	Run-Mode Clock Configuration 2 (RCC2), offset 0x070	190
Register 11:	Deep Sleep Clock Configuration (DSLPCLKCFG), offset 0x144	192
Register 12:	Device Identification 1 (DID1), offset 0x004	193
Register 13:	Device Capabilities 0 (DC0), offset 0x008	
Register 14:	Device Capabilities 1 (DC1), offset 0x010	
Register 15:	Device Capabilities 2 (DC2), offset 0x014	
Register 16:	Device Capabilities 3 (DC3), offset 0x018	
Register 17:	Device Capabilities 4 (DC4), offset 0x01C	
Register 18:	Run Mode Clock Gating Control Register 0 (RCGC0), offset 0x100	
Register 19:	Sleep Mode Clock Gating Control Register 0 (SCGC0), offset 0x110	

Register 20:	Deep Sleep Mode Clock Gating Control Register 0 (DCGC0), offset 0x120	208
Register 21:	Run Mode Clock Gating Control Register 1 (RCGC1), offset 0x104	210
Register 22:	Sleep Mode Clock Gating Control Register 1 (SCGC1), offset 0x114	212
Register 23:	Deep Sleep Mode Clock Gating Control Register 1 (DCGC1), offset 0x124	214
Register 24:	Run Mode Clock Gating Control Register 2 (RCGC2), offset 0x108	216
Register 25:	Sleep Mode Clock Gating Control Register 2 (SCGC2), offset 0x118	218
Register 26:	Deep Sleep Mode Clock Gating Control Register 2 (DCGC2), offset 0x128	220
Register 27:	Software Reset Control 0 (SRCR0), offset 0x040	222
Register 28:	Software Reset Control 1 (SRCR1), offset 0x044	223
Register 29:	Software Reset Control 2 (SRCR2), offset 0x048	224
Internal Me	mory	225
Register 1:	Flash Memory Address (FMA), offset 0x000	231
Register 2:	Flash Memory Data (FMD), offset 0x004	
Register 3:	Flash Memory Control (FMC), offset 0x008	233
Register 4:	Flash Controller Raw Interrupt Status (FCRIS), offset 0x00C	235
Register 5:	Flash Controller Interrupt Mask (FCIM), offset 0x010	
Register 6:	Flash Controller Masked Interrupt Status and Clear (FCMISC), offset 0x014	237
Register 7:	USec Reload (USECRL), offset 0x140	239
Register 8:	Flash Memory Protection Read Enable 0 (FMPRE0), offset 0x130 and 0x200	240
Register 9:	Flash Memory Protection Program Enable 0 (FMPPE0), offset 0x134 and 0x400	241
Register 10:	User Debug (USER_DBG), offset 0x1D0	242
Register 11:	User Register 0 (USER_REG0), offset 0x1E0	243
Register 12:	User Register 1 (USER_REG1), offset 0x1E4	244
Register 13:	Flash Memory Protection Read Enable 1 (FMPRE1), offset 0x204	245
Register 14:	Flash Memory Protection Read Enable 2 (FMPRE2), offset 0x208	246
Register 15:	Flash Memory Protection Read Enable 3 (FMPRE3), offset 0x20C	247
Register 16:	Flash Memory Protection Program Enable 1 (FMPPE1), offset 0x404	248
Register 17:	Flash Memory Protection Program Enable 2 (FMPPE2), offset 0x408	249
Register 18:	Flash Memory Protection Program Enable 3 (FMPPE3), offset 0x40C	250
General-Pu	rpose Input/Outputs (GPIOs)	251
Register 1:	GPIO Data (GPIODATA), offset 0x000	263
Register 2:	GPIO Direction (GPIODIR), offset 0x400	264
Register 3:	GPIO Interrupt Sense (GPIOIS), offset 0x404	265
Register 4:	GPIO Interrupt Both Edges (GPIOIBE), offset 0x408	266
Register 5:	GPIO Interrupt Event (GPIOIEV), offset 0x40C	267
Register 6:	GPIO Interrupt Mask (GPIOIM), offset 0x410	268
Register 7:	GPIO Raw Interrupt Status (GPIORIS), offset 0x414	269
Register 8:	GPIO Masked Interrupt Status (GPIOMIS), offset 0x418	270
Register 9:	GPIO Interrupt Clear (GPIOICR), offset 0x41C	271
Register 10:	GPIO Alternate Function Select (GPIOAFSEL), offset 0x420	272
Register 11:	GPIO 2-mA Drive Select (GPIODR2R), offset 0x500	274
Register 12:	GPIO 4-mA Drive Select (GPIODR4R), offset 0x504	275
Register 13:	GPIO 8-mA Drive Select (GPIODR8R), offset 0x508	
Register 14:	GPIO Open Drain Select (GPIOODR), offset 0x50C	
Register 15:	GPIO Pull-Up Select (GPIOPUR), offset 0x510	278
Register 16:	GPIO Pull-Down Select (GPIOPDR), offset 0x514	
Register 17:	GPIO Slew Rate Control Select (GPIOSLR), offset 0x518	280
Register 18:	GPIO Digital Enable (GPIODEN), offset 0x51C	281

Register 19:	GPIO Lock (GPIOLOCK), offset 0x520	282
Register 20:	GPIO Commit (GPIOCR), offset 0x524	283
Register 21:	GPIO Peripheral Identification 4 (GPIOPeriphID4), offset 0xFD0	285
Register 22:	GPIO Peripheral Identification 5 (GPIOPeriphID5), offset 0xFD4	286
Register 23:	GPIO Peripheral Identification 6 (GPIOPeriphID6), offset 0xFD8	287
Register 24:	GPIO Peripheral Identification 7 (GPIOPeriphID7), offset 0xFDC	
Register 25:	GPIO Peripheral Identification 0 (GPIOPeriphID0), offset 0xFE0	
Register 26:	GPIO Peripheral Identification 1 (GPIOPeriphID1), offset 0xFE4	
Register 27:	GPIO Peripheral Identification 2 (GPIOPeriphID2), offset 0xFE8	
Register 28:	GPIO Peripheral Identification 3 (GPIOPeriphID3), offset 0xFEC	
Register 29:	GPIO PrimeCell Identification 0 (GPIOPCellID0), offset 0xFF0	
Register 30:	GPIO PrimeCell Identification 1 (GPIOPCellID1), offset 0xFF4	294
Register 31:	GPIO PrimeCell Identification 2 (GPIOPCellID2), offset 0xFF8	295
Register 32:	GPIO PrimeCell Identification 3 (GPIOPCellID3), offset 0xFFC	
-	rpose Timers	
Register 1:	GPTM Configuration (GPTMCFG), offset 0x000	
Register 2:	GPTM TimerA Mode (GPTMTAMR), offset 0x004	
Register 3:	GPTM TimerB Mode (GPTMTBMR), offset 0x008	
Register 4:	GPTM Control (GPTMCTL), offset 0x00C	
Register 5:	GPTM Interrupt Mask (GPTMIMR), offset 0x018	
Register 6:	GPTM Raw Interrupt Status (GPTMRIS), offset 0x01C	
Register 7:	GPTM Masked Interrupt Status (GPTMMIS), offset 0x020	
Register 8:	GPTM Interrupt Clear (GPTMICR), offset 0x024	
Register 9:	GPTM TimerA Interval Load (GPTMTAILR), offset 0x028	
Register 10:	GPTM TimerB Interval Load (GPTMTBILR), offset 0x02C	
Register 11:	GPTM TimerA Match (GPTMTAMATCHR), offset 0x030	
Register 12:	GPTM TimerB Match (GPTMTBMATCHR), offset 0x034	
Register 13:	GPTM TimerA Prescale (GPTMTAPR), offset 0x038	
Register 14:	GPTM TimerB Prescale (GPTMTBPR), offset 0x03C	
Register 15:	GPTM TimerA Prescale Match (GPTMTAPMR), offset 0x040	
Register 16:	GPTM TimerB Prescale Match (GPTMTBPMR), offset 0x044	
Register 17:	GPTM TimerA (GPTMTAR), offset 0x048	
Register 18:	GPTM TimerB (GPTMTBR), offset 0x04C	
_	·	
_	Timer	333
Register 1:	Watchdog Load (WDTLOAD), offset 0x000	
Register 2:	Watchdog Value (WDTVALUE), offset 0x004	
Register 3:	Watchdog Control (WDTCTL), offset 0x008	
Register 4:	Watchdog Interrupt Clear (WDTICR), offset 0x00C	
Register 5:	Watchdog Raw Interrupt Status (WDTRIS), offset 0x010	
Register 6:	Watchdog Masked Interrupt Status (WDTMIS), offset 0x014	
Register 7:	Watchdog Test (WDTTEST), offset 0x418	
Register 8:	Watchdog Lock (WDTLOCK), offset 0xC00	
Register 9:	Watchdog Peripheral Identification 4 (WDTPeriphID4), offset 0xFD0	
Register 10:	Watchdog Peripheral Identification 5 (WDTPeriphID5), offset 0xFD4	
Register 11:	Watchdog Peripheral Identification 6 (WDTPeriphID6), offset 0xFD8	
Register 12:	Watchdog Peripheral Identification 7 (WDTPeriphID7), offset 0xFDC	
Register 13:	Watchdog Peripheral Identification 0 (WDTPeriphID0), offset 0xFE0	
Register 14:	Watchdog Peripheral Identification 1 (WDTPeriphID1), offset 0xFE4	350

Register 15:	Watchdog Peripheral Identification 2 (WDTPeriphID2), offset 0xFE8	351
Register 16:	Watchdog Peripheral Identification 3 (WDTPeriphID3), offset 0xFEC	352
Register 17:	Watchdog PrimeCell Identification 0 (WDTPCellID0), offset 0xFF0	353
Register 18:	Watchdog PrimeCell Identification 1 (WDTPCellID1), offset 0xFF4	354
Register 19:	Watchdog PrimeCell Identification 2 (WDTPCellID2), offset 0xFF8	355
Register 20:	Watchdog PrimeCell Identification 3 (WDTPCellID3 ), offset 0xFFC	356
Analog-to-[	Digital Converter (ADC)	357
Register 1:	ADC Active Sample Sequencer (ADCACTSS), offset 0x000	
Register 2:	ADC Raw Interrupt Status (ADCRIS), offset 0x004	
Register 3:	ADC Interrupt Mask (ADCIM), offset 0x008	369
Register 4:	ADC Interrupt Status and Clear (ADCISC), offset 0x00C	
Register 5:	ADC Overflow Status (ADCOSTAT), offset 0x010	
Register 6:	ADC Event Multiplexer Select (ADCEMUX), offset 0x014	
Register 7:	ADC Underflow Status (ADCUSTAT), offset 0x018	
Register 8:	ADC Sample Sequencer Priority (ADCSSPRI), offset 0x020	376
Register 9:	ADC Processor Sample Sequence Initiate (ADCPSSI), offset 0x028	378
Register 10:	ADC Sample Averaging Control (ADCSAC), offset 0x030	379
Register 11:	ADC Sample Sequence Input Multiplexer Select 0 (ADCSSMUX0), offset 0x040	380
Register 12:	ADC Sample Sequence Control 0 (ADCSSCTL0), offset 0x044	382
Register 13:	ADC Sample Sequence Result FIFO 0 (ADCSSFIFO0), offset 0x048	385
Register 14:	ADC Sample Sequence Result FIFO 1 (ADCSSFIFO1), offset 0x068	385
Register 15:	ADC Sample Sequence Result FIFO 2 (ADCSSFIFO2), offset 0x088	385
Register 16:	ADC Sample Sequence Result FIFO 3 (ADCSSFIFO3), offset 0x0A8	385
Register 17:	ADC Sample Sequence FIFO 0 Status (ADCSSFSTAT0), offset 0x04C	386
Register 18:	ADC Sample Sequence FIFO 1 Status (ADCSSFSTAT1), offset 0x06C	386
Register 19:	ADC Sample Sequence FIFO 2 Status (ADCSSFSTAT2), offset 0x08C	386
Register 20:	ADC Sample Sequence FIFO 3 Status (ADCSSFSTAT3), offset 0x0AC	386
Register 21:	ADC Sample Sequence Input Multiplexer Select 1 (ADCSSMUX1), offset 0x060	387
Register 22:	ADC Sample Sequence Input Multiplexer Select 2 (ADCSSMUX2), offset 0x080	387
Register 23:	ADC Sample Sequence Control 1 (ADCSSCTL1), offset 0x064	388
Register 24:	ADC Sample Sequence Control 2 (ADCSSCTL2), offset 0x084	388
Register 25:	ADC Sample Sequence Input Multiplexer Select 3 (ADCSSMUX3), offset 0x0A0	390
Register 26:	ADC Sample Sequence Control 3 (ADCSSCTL3), offset 0x0A4	391
Register 27:	ADC Test Mode Loopback (ADCTMLB), offset 0x100	392
Universal A	synchronous Receivers/Transmitters (UARTs)	393
Register 1:	UART Data (UARTDR), offset 0x000	
Register 2:	UART Receive Status/Error Clear (UARTRSR/UARTECR), offset 0x004	404
Register 3:	UART Flag (UARTFR), offset 0x018	406
Register 4:	UART IrDA Low-Power Register (UARTILPR), offset 0x020	408
Register 5:	UART Integer Baud-Rate Divisor (UARTIBRD), offset 0x024	409
Register 6:	UART Fractional Baud-Rate Divisor (UARTFBRD), offset 0x028	
Register 7:	UART Line Control (UARTLCRH), offset 0x02C	411
Register 8:	UART Control (UARTCTL), offset 0x030	413
Register 9:	UART Interrupt FIFO Level Select (UARTIFLS), offset 0x034	
Register 10:	UART Interrupt Mask (UARTIM), offset 0x038	
Register 11:	UART Raw Interrupt Status (UARTRIS), offset 0x03C	
Register 12:	UART Masked Interrupt Status (UARTMIS), offset 0x040	420
Register 13:	UART Interrupt Clear (UARTICR), offset 0x044	

Register 14:	UART Peripheral Identification 4 (UARTPeriphID4), offset 0xFD0	423
Register 15:	UART Peripheral Identification 5 (UARTPeriphID5), offset 0xFD4	424
Register 16:	UART Peripheral Identification 6 (UARTPeriphID6), offset 0xFD8	425
Register 17:	UART Peripheral Identification 7 (UARTPeriphID7), offset 0xFDC	426
Register 18:	UART Peripheral Identification 0 (UARTPeriphID0), offset 0xFE0	427
Register 19:	UART Peripheral Identification 1 (UARTPeriphID1), offset 0xFE4	428
Register 20:	UART Peripheral Identification 2 (UARTPeriphID2), offset 0xFE8	429
Register 21:	UART Peripheral Identification 3 (UARTPeriphID3), offset 0xFEC	430
Register 22:	UART PrimeCell Identification 0 (UARTPCellID0), offset 0xFF0	431
Register 23:	UART PrimeCell Identification 1 (UARTPCellID1), offset 0xFF4	432
Register 24:	UART PrimeCell Identification 2 (UARTPCellID2), offset 0xFF8	433
Register 25:	UART PrimeCell Identification 3 (UARTPCelIID3), offset 0xFFC	434
Synchrono	us Serial Interface (SSI)	435
Register 1:	SSI Control 0 (SSICR0), offset 0x000	448
Register 2:	SSI Control 1 (SSICR1), offset 0x004	450
Register 3:	SSI Data (SSIDR), offset 0x008	452
Register 4:	SSI Status (SSISR), offset 0x00C	453
Register 5:	SSI Clock Prescale (SSICPSR), offset 0x010	455
Register 6:	SSI Interrupt Mask (SSIIM), offset 0x014	456
Register 7:	SSI Raw Interrupt Status (SSIRIS), offset 0x018	458
Register 8:	SSI Masked Interrupt Status (SSIMIS), offset 0x01C	459
Register 9:	SSI Interrupt Clear (SSIICR), offset 0x020	460
Register 10:	SSI Peripheral Identification 4 (SSIPeriphID4), offset 0xFD0	461
Register 11:	SSI Peripheral Identification 5 (SSIPeriphID5), offset 0xFD4	462
Register 12:	SSI Peripheral Identification 6 (SSIPeriphID6), offset 0xFD8	463
Register 13:	SSI Peripheral Identification 7 (SSIPeriphID7), offset 0xFDC	464
Register 14:	SSI Peripheral Identification 0 (SSIPeriphID0), offset 0xFE0	465
Register 15:	SSI Peripheral Identification 1 (SSIPeriphID1), offset 0xFE4	466
Register 16:	SSI Peripheral Identification 2 (SSIPeriphID2), offset 0xFE8	
Register 17:	SSI Peripheral Identification 3 (SSIPeriphID3), offset 0xFEC	468
Register 18:	SSI PrimeCell Identification 0 (SSIPCellID0), offset 0xFF0	469
Register 19:	SSI PrimeCell Identification 1 (SSIPCellID1), offset 0xFF4	470
Register 20:	SSI PrimeCell Identification 2 (SSIPCellID2), offset 0xFF8	471
Register 21:	SSI PrimeCell Identification 3 (SSIPCelIID3), offset 0xFFC	472
Ethernet Co	ontroller	473
Register 1:	Ethernet MAC Raw Interrupt Status/Acknowledge (MACRIS/MACIACK), offset 0x000	
Register 2:	Ethernet MAC Interrupt Mask (MACIM), offset 0x004	
Register 3:	Ethernet MAC Receive Control (MACRCTL), offset 0x008	
Register 4:	Ethernet MAC Transmit Control (MACTCTL), offset 0x00C	
Register 5:	Ethernet MAC Data (MACDATA), offset 0x010	491
Register 6:	Ethernet MAC Individual Address 0 (MACIA0), offset 0x014	
Register 7:	Ethernet MAC Individual Address 1 (MACIA1), offset 0x018	
Register 8:	Ethernet MAC Threshold (MACTHR), offset 0x01C	
Register 9:	Ethernet MAC Management Control (MACMCTL), offset 0x020	
Register 10:	Ethernet MAC Management Divider (MACMDV), offset 0x024	
Register 11:	Ethernet MAC Management Transmit Data (MACMTXD), offset 0x02C	
Register 12:	Ethernet MAC Management Receive Data (MACMRXD), offset 0x030	
Register 13:	Ethernet MAC Number of Packets (MACNP). offset 0x034	501

Register 14:	Ethernet MAC Transmission Request (MACTR), offset 0x038	502
Register 15:	Ethernet PHY Management Register 0 – Control (MR0), address 0x00	503
Register 16:	Ethernet PHY Management Register 1 – Status (MR1), address 0x01	505
Register 17:	Ethernet PHY Management Register 2 – PHY Identifier 1 (MR2), address 0x02	507
Register 18:	Ethernet PHY Management Register 3 – PHY Identifier 2 (MR3), address 0x03	508
Register 19:	Ethernet PHY Management Register 4 – Auto-Negotiation Advertisement (MR4), address	
	0x04	509
Register 20:	Ethernet PHY Management Register 5 – Auto-Negotiation Link Partner Base Page Ability	
	(MR5), address 0x05	511
Register 21:	Ethernet PHY Management Register 6 – Auto-Negotiation Expansion (MR6), address	E40
Dagieter 22:	0x06	512
Register 22:	Ethernet PHY Management Register 16 – Vendor-Specific (MR16), address 0x10	513
Register 23:	Ethernet PHY Management Register 17 – Interrupt Control/Status (MR17), address 0x11	515
Register 24:	Ethernet PHY Management Register 18 – Diagnostic (MR18), address 0x12	
Register 25:	Ethernet PHY Management Register 19 – Transceiver Control (MR19), address 0x13	
Register 26:	Ethernet PHY Management Register 23 – LED Configuration (MR23), address 0x17	519
Register 27:	Ethernet PHY Management Register 24 -MDI/MDIX Control (MR24), address 0x18	520
Analog Con	nparators	521
Register 1:	Analog Comparator Masked Interrupt Status (ACMIS), offset 0x000	526
Register 2:	Analog Comparator Raw Interrupt Status (ACRIS), offset 0x004	527
Register 3:	Analog Comparator Interrupt Enable (ACINTEN), offset 0x008	528
Register 4:	Analog Comparator Reference Voltage Control (ACREFCTL), offset 0x010	529
Register 5:	Analog Comparator Status 0 (ACSTAT0), offset 0x020	530
Register 6:	Analog Comparator Status 1 (ACSTAT1), offset 0x040	530
Register 7:	Analog Comparator Control 0 (ACCTL0), offset 0x024	531
Register 8:	Analog Comparator Control 1 (ACCTL1), offset 0x044	531

# **Revision History**

The revision history table notes changes made between the indicated revisions of the LM3S6422 data sheet.

**Table 1. Revision History** 

Date	Revision	Description
November 2011	11108	■ Added module-specific pin tables to each chapter in the new Signal Description sections.
		■ In Timer chapter, clarified that in 16-Bit Input Edge Time Mode, the timer is capable of capturing three types of events: rising edge, falling edge, or both.
		■ In UART chapter, clarified interrupt behavior.
		■ In SSI chapter, corrected SSICIk in the figure "Synchronous Serial Frame Format (Single Transfer)".
		■ In Signal Tables chapter:
		Corrected pin numbers in table "Connections for Unused Signals" (other pin tables were correct).
		■ In Electrical Characteristics chapter:
		<ul> <li>Added parameter "Input voltage for a GPIO configured as an analog input" to the "Maximum Ratings" table.</li> </ul>
		Corrected Nom values for parameters "TCK clock Low time" and "TCK clock High time" in "JTAG Characteristics" table.
		<ul> <li>Corrected missing values for "Conversion time" and "Conversion rate" parameters in "ADC Characteristics" table.</li> </ul>
		Additional minor data sheet clarifications and corrections.
January 2011	9102	■ In Application Interrupt and Reset Control (APINT) register, changed bit name from SYSRESETREQ to SYSRESREQ.
		■ Added DEBUG (Debug Priority) bit field to System Handler Priority 3 (SYSPRI3) register.
		■ Added "Reset Sources" table to System Control chapter.
		■ Corrected GPIOAMSEL bit field in GPIO Analog Mode Select (GPIOAMSEL) register to be four-bits wide, bits[7:4].
		Removed mention of false-start bit detection in the UART chapter. This feature is not supported.
		■ Added note that specific module clocks must be enabled before that module's registers can be programmed. There must be a delay of 3 system clocks after the module clock is enabled before any of that module's registers are accessed.
		■ Added GNDPHY and VCCPHY to Connections for Unused Signals tables.
		■ Corrected nonlinearity and offset error parameters (E <sub>L</sub> , E <sub>D</sub> and E <sub>O</sub> ) in ADC Characteristics table.
		<ul> <li>Added specification for maximum input voltage on a non-power pin when the microcontroller is unpowered (V<sub>NON</sub> parameter in Maximum Ratings table).</li> </ul>
		■ Additional minor data sheet clarifications and corrections.

Table 1. Revision History (continued)

Date	Revision	Description
September 2010	7787	■ Reorganized ARM Cortex-M3 Processor Core, Memory Map and Interrupts chapters, creating two new chapters, The Cortex-M3 Processor and Cortex-M3 Peripherals. Much additional content was added, including all the Cortex-M3 registers.
		■ Changed register names to be consistent with StellarisWare® names: the Cortex-M3 Interrupt Control and Status (ICSR) register to the Interrupt Control and State (INTCTRL) register, and the Cortex-M3 Interrupt Set Enable (SETNA) register to the Interrupt 0-31 Set Enable (EN0) register.
		■ Added clarification of instruction execution during Flash operations.
		■ Modified Figure 7-1 on page 256 to clarify operation of the GPIO inputs when used as an alternate function.
		■ Corrected GPIOAMSEL bit field in GPIO Analog Mode Select (GPIOAMSEL) register to be eight-bits wide, bits[7:0].
		■ Added caution not to apply a Low value to PB7 when debugging; a Low value on the pin causes the JTAG controller to be reset, resulting in a loss of JTAG communication.
		■ In General-Purpose Timers chapter, clarified operation of the 32-bit RTC mode.
		■ In Electrical Characteristics chapter:  - Added I <sub>LKG</sub> parameter (GPIO input leakage current) to Table 18-4 on page 561.  - Corrected values for t <sub>CLKRF</sub> parameter (SSIClk rise/fall time) in Table 18-19 on page 570.  - Added "Ethernet Controller DC Characteristics" table (see Table 18-7 on page 563).
		■ Added dimensions for Tray and Tape and Reel shipping mediums.
June 2010	7393	Corrected base address for SRAM in architectural overview chapter.
		■ Clarified system clock operation, adding content to "Clock Control" on page 169.
		■ In Signal Tables chapter, added table "Connections for Unused Signals."
		■ In "Thermal Characteristics" table, corrected thermal resistance value from 34 to 32.
		■ In "Reset Characteristics" table, corrected value for supply voltage (VDD) rise time.
		Additional minor data sheet clarifications and corrections.
April 2010	7007	Added caution note to the I <sup>2</sup> C Master Timer Period (I2CMTPR) register description and changed field width to 7 bits.
		■ Removed erroneous text about restoring the Flash Protection registers.
		■ Added note about RST signal routing.
		■ Clarified the function of the TnSTALL bit in the GPTMCTL register.
		■ Corrected XTALNPHY pin description.
		■ Additional minor data sheet clarifications and corrections.

Table 1. Revision History (continued)

Date	Revision	Description
January 2010	6712	■ In "System Control" section, clarified Debug Access Port operation after Sleep modes.
		Clarified wording on Flash memory access errors.
		■ Added section on Flash interrupts.
		■ Changed the reset value of the ADC Sample Sequence Result FIFO n (ADCSSFIFOn) registers to be indeterminate.
		■ Clarified operation of SSI transmit FIFO.
		■ Made these changes to the Operating Characteristics chapter:
		Added storage temperature ratings to "Temperature Characteristics" table
		Added "ESD Absolute Maximum Ratings" table
		■ Made these changes to the Electrical Characteristics chapter:
		In "Flash Memory Characteristics" table, corrected Mass erase time
		Added sleep and deep-sleep wake-up times ("Sleep Modes AC Characteristics" table)
		In "Reset Characteristics" table, corrected units for supply voltage (VDD) rise time
October 2009	6462	■ Deleted MAXADCSPD bit field from <b>DCGC0</b> register as it is not applicable in Deep-Sleep mode.
		■ Deleted reset value for 16-bit mode from <b>GPTMTAILR</b> , <b>GPTMTAMATCHR</b> , and <b>GPTMTAR</b> registers because the module resets in 32-bit mode.
		■ Clarified PWM source for ADC triggering.
		■ Made these changes to the Electrical Characteristics chapter:
		<ul> <li>Removed V<sub>SIH</sub> and V<sub>SIL</sub> parameters from Operating Conditions table.</li> </ul>
		Added table showing actual PLL frequency depending on input crystal.
		<ul> <li>Changed the name of the t<sub>HIB_REG_WRITE</sub> parameter to t<sub>HIB_REG_ACCESS</sub>.</li> </ul>
		Revised ADC electrical specifications to clarify, including reorganizing and adding new data.
		Changed SSI set up and hold times to be expressed in system clocks, not ns.
July 2009	5920	Corrected ordering numbers.
July 2009	5902	■ Clarified Power-on reset and RST pin operation; added new diagrams.
		Clarified explanation of nonvolatile register programming in Internal Memory chapter.
		■ Added explanation of reset value to FMPRE0/1/2/3, FMPPE0/1/2/3, USER_DBG, and USER_REG0/1 registers.
		■ Added description for Ethernet PHY power-saving modes.
		■ Corrected the reset values for bits 6 and 7 in the Ethernet MR24 register.
		■ Changed buffer type for WAKE pin to TTL and HIB pin to OD.
		■ In ADC characteristics table, changed Max value for GAIN parameter from ±1 to ±3 and added E <sub>IR</sub> (Internal voltage reference error) parameter.
		Additional minor data sheet clarifications and corrections.

Table 1. Revision History (continued)

Date	Revision	Description
April 2009	5367	■ Added JTAG/SWD clarification (see "Communication with JTAG/SWD" on page 157).
		■ Added clarification that the PLL operates at 400 MHz, but is divided by two prior to the application of the output divisor.
		■ Added "GPIO Module DC Characteristics" table (see Table 18-4 on page 561).
		Additional minor data sheet clarifications and corrections.
January 2009	4660	■ Corrected bit type for RELOAD bit field in SysTick Reload Value register; changed to R/W.
		<ul> <li>Clarification added as to what happens when the SSI in slave mode is required to transmit but there is no data in the TX FIFO.</li> </ul>
		<ul> <li>Added "Hardware Configuration" section to Ethernet Controller chapter.</li> </ul>
		Additional minor data sheet clarifications and corrections.
November 2008	4283	Revised High-Level Block Diagram.
		Additional minor data sheet clarifications and corrections were made.
October 2008	4149	<ul> <li>Corrected values for DSOSCSRC bit field in Deep Sleep Clock Configuration (DSLPCLKCFG) register.</li> </ul>
		■ The FMA value for the <b>FMPRE3</b> register was incorrect in the Flash Resident Registers table in the Internal Memory chapter. The correct value is 0x0000.0006.
		■ In the Ethernet chapter, major improvements were made including a rewrite of the conceptual information and the addition of new figures to clarify how to use the Ethernet Controller interface.
		■ Incorrect Comparator Operating Modes tables were removed from the Analog Comparators chapter.
August 2008	3447	Added note on clearing interrupts to Interrupts chapter.
		Added Power Architecture diagram to System Control chapter.
		Additional minor data sheet clarifications and corrections.
July 2008	3108	■ Corrected resistor value in ERBIAS signal description.
		Additional minor data sheet clarifications and corrections.
May 2008	2972	■ The 108-Ball BGA pin diagram and pin tables had an error. The following signals were erroneously indicated as available and have now been changed to a No Connect (NC):
		<ul> <li>Ball C1: Changed PE7 to NC</li> </ul>
		Ball C2: Changed ₽E6 to NC
		■ As noted in the PCN, three of the nine Ethernet LED configuration options are no longer supported: TX Activity (0x2), RX Activity (0x3), and Collision (0x4). These values for the LED0 and LED1 bit fields in the MR23 register are now marked as reserved.
		■ As noted in the PCN, the option to provide VDD25 power from external sources was removed. Use the LDO output as the source of VDD25 input.
		As noted in the PCN, pin 41 (ball K3 on the BGA package) was renamed from GNDPHY to ERBIAS. A 12.4-kΩ resistor should be connected between ERBIAS and ground to accommodate future device revisions (see "Functional Description" on page 476).
		<ul> <li>Additional minor data sheet clarifications and corrections.</li> </ul>

Table 1. Revision History (continued)

Date	Revision	Description
April 2008	2881	■ The O <sub>JA</sub> value was changed from 55.3 to 34 in the "Thermal Characteristics" table in the Operating Characteristics chapter.
		■ Bit 31 of the <b>DC3</b> register was incorrectly described in prior versions of the data sheet. A reset of 1 indicates that an even CCP pin is present and can be used as a 32-KHz input clock.
		■ Values for I <sub>DD_HIBERNATE</sub> were added to the "Detailed Power Specifications" table in the "Electrical Characteristics" chapter.
		■ The "Hibernation Module DC Electricals" table was added to the "Electrical Characteristics" chapter.
		■ The maximum value on Core supply voltage (V <sub>DD25</sub> ) in the "Maximum Ratings" table in the "Electrical Characteristics" chapter was changed from 4 to 3.
		■ The operational frequency of the internal 30-kHz oscillator clock source is 30 kHz ± 50% (prior data sheets incorrectly noted it as 30 kHz ± 30%).
		A value of 0x3 in bits 5:4 of the MISC register (OSCSRC) indicates the 30-KHz internal oscillator is the input source for the oscillator. Prior data sheets incorrectly noted 0x3 as a reserved value.
		■ The reset for bits 6:4 of the RCC2 register (OSCSRC2) is 0x1 (IOSC). Prior data sheets incorrectly noted the reset was 0x0 (MOSC).
		■ A note on high-current applications was added to the GPIO chapter:
		For special high-current applications, the GPIO output buffers may be used with the following restrictions. With the GPIO pins configured as 8-mA output drivers, a total of four GPIO outputs may be used to sink current loads up to 18 mA each. At 18-mA sink current loading, the VOL value is specified as 1.2 V. The high-current GPIO package pins must be selected such that there are only a maximum of two per side of the physical package or BGA pin group with the total number of high-current GPIO outputs not exceeding four for the entire package.
		A note on Schmitt inputs was added to the GPIO chapter:
		Pins configured as digital inputs are Schmitt-triggered.
		■ The Buffer type on the WAKE pin changed from OD to - in the Signal Tables.
		■ The "Differential Sampling Range" figures in the ADC chapter were clarified.
		■ The last revision of the data sheet (revision 2550) introduced two errors that have now been corrected:
		The LQFP pin diagrams and pin tables were missing the comparator positive and negative input pins.
		The base address was listed incorrectly in the FMPRE0 and FMPPE0 register bit diagrams.
		Additional minor data sheet clarifications and corrections.
March 2008	2550	Started tracking revision history.

## **About This Document**

This data sheet provides reference information for the LM3S6422 microcontroller, describing the functional blocks of the system-on-chip (SoC) device designed around the ARM® Cortex™-M3 core.

### **Audience**

This manual is intended for system software developers, hardware designers, and application developers.

## **About This Manual**

This document is organized into sections that correspond to each major feature.

### **Related Documents**

The following related documents are available on the Stellaris® web site at www.ti.com/stellaris:

- Stellaris® Errata
- ARM® Cortex™-M3 Errata
- Cortex™-M3/M4 Instruction Set Technical User's Manual
- Stellaris® Graphics Library User's Guide
- Stellaris® Peripheral Driver Library User's Guide

The following related documents are also referenced:

- ARM® Debug Interface V5 Architecture Specification
- ARM® Embedded Trace Macrocell Architecture Specification
- IEEE Standard 1149.1-Test Access Port and Boundary-Scan Architecture

This documentation list was current as of publication date. Please check the web site for additional documentation, including application notes and white papers.

## **Documentation Conventions**

This document uses the conventions shown in Table 2 on page 27.

**Table 2. Documentation Conventions** 

Notation	Meaning
General Register Nota	ition
REGISTER	APB registers are indicated in uppercase bold. For example, <b>PBORCTL</b> is the Power-On and Brown-Out Reset Control register. If a register name contains a lowercase n, it represents more than one register. For example, <b>SRCRn</b> represents any (or all) of the three Software Reset Control registers: <b>SRCR0</b> , <b>SRCR1</b> , and <b>SRCR2</b> .
bit	A single bit in a register.
bit field	Two or more consecutive and related bits.
offset 0xnnn	A hexadecimal increment to a register's address, relative to that module's base address as specified in Table 2-4 on page 63.
Register N	Registers are numbered consecutively throughout the document to aid in referencing them. The register number has no meaning to software.
reserved	Register bits marked <i>reserved</i> are reserved for future use. In most cases, reserved bits are set to 0; however, user software should not rely on the value of a reserved bit. To provide software compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
yy:xx	The range of register bits inclusive from xx to yy. For example, 31:15 means bits 15 through 31 in that register.
Register Bit/Field Types	This value in the register bit diagram indicates whether software running on the controller can change the value of the bit field.
RC	Software can read this field. The bit or field is cleared by hardware after reading the bit/field.
RO	Software can read this field. Always write the chip reset value.
R/W	Software can read or write this field.
R/WC	Software can read or write this field. Writing to it with any value clears the register.
R/W1C	Software can read or write this field. A write of a 0 to a W1C bit does not affect the bit value in the register. A write of a 1 clears the value of the bit in the register; the remaining bits remain unchanged.
	This register type is primarily used for clearing interrupt status bits where the read operation provides the interrupt status and the write of the read value clears only the interrupts being reported at the time the register was read.
R/W1S	Software can read or write a 1 to this field. A write of a 0 to a R/W1S bit does not affect the bit value in the register.
W1C	Software can write this field. A write of a 0 to a W1C bit does not affect the bit value in the register. A write of a 1 clears the value of the bit in the register; the remaining bits remain unchanged. A read of the register returns no meaningful data.
	This register is typically used to clear the corresponding bit in an interrupt register.
WO	Only a write by software is valid; a read of the register returns no meaningful data.
Register Bit/Field Reset Value	This value in the register bit diagram shows the bit/field value after any reset, unless noted.
0	Bit cleared to 0 on chip reset.
1	Bit set to 1 on chip reset.
-	Nondeterministic.
Pin/Signal Notation	
[]	Pin alternate function; a pin defaults to the signal without the brackets.
pin	Refers to the physical connection on the package.
signal	Refers to the electrical signal encoding of a pin.

Table 2. Documentation Conventions (continued)

Notation	Meaning
assert a signal	Change the value of the signal from the logically False state to the logically True state. For active High signals, the asserted signal value is 1 (High); for active Low signals, the asserted signal value is 0 (Low). The active polarity (High or Low) is defined by the signal name (see SIGNAL and SIGNAL below).
deassert a signal	Change the value of the signal from the logically True state to the logically False state.
SIGNAL	Signal names are in uppercase and in the Courier font. An overbar on a signal name indicates that it is active Low. To assert SIGNAL is to drive it Low; to deassert SIGNAL is to drive it High.
SIGNAL	Signal names are in uppercase and in the Courier font. An active High signal has no overbar. To assert Signal is to drive it High; to deassert Signal is to drive it Low.
Numbers	
Х	An uppercase X indicates any of several values is allowed, where X can be any legal pattern. For example, a binary value of 0X00 can be either 0100 or 0000, a hex value of 0xX is 0x0 or 0x1, and so on.
0x	Hexadecimal numbers have a prefix of 0x. For example, 0x00FF is the hexadecimal number FF.
	All other numbers within register tables are assumed to be binary. Within conceptual information, binary numbers are indicated with a b suffix, for example, 1011b, and decimal numbers are written without a prefix or suffix.

## 1 Architectural Overview

The Stellaris<sup>®</sup> family of microcontrollers—the first ARM® Cortex<sup>™</sup>-M3 based controllers—brings high-performance 32-bit computing to cost-sensitive embedded microcontroller applications. These pioneering parts deliver customers 32-bit performance at a cost equivalent to legacy 8- and 16-bit devices, all in a package with a small footprint.

The Stellaris family offers efficient performance and extensive integration, favorably positioning the device into cost-conscious applications requiring significant control-processing and connectivity capabilities. The Stellaris LM3S6000 series combines both a 10/100 Ethernet Media Access Control (MAC) and Physical (PHY) layer, marking the first time that integrated connectivity is available with an ARM Cortex-M3 MCU and the only integrated 10/100 Ethernet MAC and PHY available in an ARM architecture MCU.

The LM3S6422 microcontroller is targeted for industrial applications, including remote monitoring, electronic point-of-sale machines, test and measurement equipment, network appliances and switches, factory automation, HVAC and building control, gaming equipment, motion control, medical instrumentation, and fire and security.

In addition, the LM3S6422 microcontroller offers the advantages of ARM's widely available development tools, System-on-Chip (SoC) infrastructure IP applications, and a large user community. Additionally, the microcontroller uses ARM's Thumb®-compatible Thumb-2 instruction set to reduce memory requirements and, thereby, cost. Finally, the LM3S6422 microcontroller is code-compatible to all members of the extensive Stellaris family; providing flexibility to fit our customers' precise needs.

Texas Instruments offers a complete solution to get to market quickly, with evaluation and development boards, white papers and application notes, an easy-to-use peripheral driver library, and a strong support, sales, and distributor network. See "Ordering and Contact Information" on page 599 for ordering information for Stellaris family devices.

## 1.1 Product Features

The LM3S6422 microcontroller includes the following product features:

- 32-Bit RISC Performance
  - 32-bit ARM® Cortex™-M3 v7M architecture optimized for small-footprint embedded applications
  - System timer (SysTick), providing a simple, 24-bit clear-on-write, decrementing, wrap-on-zero counter with a flexible control mechanism
  - Thumb®-compatible Thumb-2-only instruction set processor core for high code density
  - 25-MHz operation
  - Hardware-division and single-cycle-multiplication
  - Integrated Nested Vectored Interrupt Controller (NVIC) providing deterministic interrupt handling
  - 25 interrupts with eight priority levels

- Memory protection unit (MPU), providing a privileged mode for protected operating system functionality
- Unaligned data access, enabling data to be efficiently packed into memory
- Atomic bit manipulation (bit-banding), delivering maximum memory utilization and streamlined peripheral control
- ARM® Cortex™-M3 Processor Core
  - Compact core.
  - Thumb-2 instruction set, delivering the high-performance expected of an ARM core in the memory size usually associated with 8- and 16-bit devices; typically in the range of a few kilobytes of memory for microcontroller class applications.
  - Rapid application execution through Harvard architecture characterized by separate buses for instruction and data.
  - Exceptional interrupt handling, by implementing the register manipulations required for handling an interrupt in hardware.
  - Deterministic, fast interrupt processing: always 12 cycles, or just 6 cycles with tail-chaining
  - Memory protection unit (MPU) to provide a privileged mode of operation for complex applications.
  - Migration from the ARM7™ processor family for better performance and power efficiency.
  - Full-featured debug solution
    - Serial Wire JTAG Debug Port (SWJ-DP)
    - Flash Patch and Breakpoint (FPB) unit for implementing breakpoints
    - Data Watchpoint and Trigger (DWT) unit for implementing watchpoints, trigger resources, and system profiling
    - Instrumentation Trace Macrocell (ITM) for support of printf style debugging
    - Trace Port Interface Unit (TPIU) for bridging to a Trace Port Analyzer
  - Optimized for single-cycle flash usage
  - Three sleep modes with clock gating for low power
  - Single-cycle multiply instruction and hardware divide
  - Atomic operations
  - ARM Thumb2 mixed 16-/32-bit instruction set
  - 1.25 DMIPS/MHz
- JTAG

- IEEE 1149.1-1990 compatible Test Access Port (TAP) controller
- Four-bit Instruction Register (IR) chain for storing JTAG instructions
- IEEE standard instructions: BYPASS, IDCODE, SAMPLE/PRELOAD, EXTEST and INTEST
- ARM additional instructions: APACC, DPACC and ABORT
- Integrated ARM Serial Wire Debug (SWD)

### Internal Memory

- 96 KB single-cycle flash
  - User-managed flash block protection on a 2-KB block basis
  - · User-managed flash data programming
  - User-defined and managed flash-protection block
- 32 KB single-cycle SRAM

#### GPIOs

- 12-34 GPIOs, depending on configuration
- 5-V-tolerant in input configuration
- Fast toggle capable of a change every two clock cycles
- Programmable control for GPIO interrupts
  - · Interrupt generation masking
  - · Edge-triggered on rising, falling, or both
  - · Level-sensitive on High or Low values
- Bit masking in both read and write operations through address lines
- Can initiate an ADC sample sequence
- Pins configured as digital inputs are Schmitt-triggered.
- Programmable control for GPIO pad configuration
  - · Weak pull-up or pull-down resistors
  - 2-mA, 4-mA, and 8-mA pad drive for digital communication; up to four pads can be configured with an 18-mA pad drive for high-current applications
  - Slew rate control for the 8-mA drive
  - Open drain enables
  - Digital input enables

### ■ General-Purpose Timers

- Three General-Purpose Timer Modules (GPTM), each of which provides two 16-bit timers/counters. Each GPTM can be configured to operate independently:
  - As a single 32-bit timer
  - As one 32-bit Real-Time Clock (RTC) to event capture
  - For Pulse Width Modulation (PWM)
  - To trigger analog-to-digital conversions
- 32-bit Timer modes
  - Programmable one-shot timer
  - Programmable periodic timer
  - Real-Time Clock when using an external 32.768-KHz clock as the input
  - User-enabled stalling when the controller asserts CPU Halt flag during debug
  - ADC event trigger
- 16-bit Timer modes
  - General-purpose timer function with an 8-bit prescaler (for one-shot and periodic modes only)
  - Programmable one-shot timer
  - · Programmable periodic timer
  - User-enabled stalling when the controller asserts CPU Halt flag during debug
  - ADC event trigger
- 16-bit Input Capture modes
  - Input edge count capture
  - Input edge time capture
- 16-bit PWM mode
  - Simple PWM mode with software-programmable output inversion of the PWM signal
- ARM FiRM-compliant Watchdog Timer
  - 32-bit down counter with a programmable load register
  - Separate watchdog clock with an enable
  - Programmable interrupt generation logic with interrupt masking
  - Lock register protection from runaway software

- Reset generation logic with an enable/disable
- User-enabled stalling when the controller asserts the CPU Halt flag during debug

#### ADC

- Two analog input channels
- Single-ended and differential-input configurations
- On-chip internal temperature sensor
- Sample rate of 250 thousand samples/second
- Flexible, configurable analog-to-digital conversion
- Four programmable sample conversion sequences from one to eight entries long, with corresponding conversion result FIFOs
- Flexible trigger control
  - Controller (software)
  - Timers
  - Analog Comparators
  - GPIO
- Hardware averaging of up to 64 samples for improved accuracy
- Converter uses an internal 3-V reference
- Power and ground for the analog circuitry is separate from the digital power and ground

#### UART

- Fully programmable 16C550-type UART with IrDA support
- Separate 16x8 transmit (TX) and receive (RX) FIFOs to reduce CPU interrupt service loading
- Programmable baud-rate generator allowing speeds up to 1.5625 Mbps
- Programmable FIFO length, including 1-byte deep operation providing conventional double-buffered interface
- FIFO trigger levels of 1/8, 1/4, 1/2, 3/4, and 7/8
- Standard asynchronous communication bits for start, stop, and parity
- Line-break generation and detection
- Fully programmable serial interface characteristics
  - 5, 6, 7, or 8 data bits
  - Even, odd, stick, or no-parity bit generation/detection

- 1 or 2 stop bit generation
- IrDA serial-IR (SIR) encoder/decoder providing
  - Programmable use of IrDA Serial Infrared (SIR) or UART input/output
  - Support of IrDA SIR encoder/decoder functions for data rates up to 115.2 Kbps half-duplex
  - Support of normal 3/16 and low-power (1.41-2.23 μs) bit durations
  - Programmable internal clock generator enabling division of reference clock by 1 to 256 for low-power mode bit duration
- Synchronous Serial Interface (SSI)
  - Master or slave operation
  - Programmable clock bit rate and prescale
  - Separate transmit and receive FIFOs, 16 bits wide, 8 locations deep
  - Programmable interface operation for Freescale SPI, MICROWIRE, or Texas Instruments synchronous serial interfaces
  - Programmable data frame size from 4 to 16 bits
  - Internal loopback test mode for diagnostic/debug testing
- 10/100 Ethernet Controller
  - Conforms to the IEEE 802.3-2002 specification
    - 10BASE-T/100BASE-TX IEEE-802.3 compliant. Requires only a dual 1:1 isolation transformer interface to the line
    - 10BASE-T/100BASE-TX ENDEC, 100BASE-TX scrambler/descrambler
    - Full-featured auto-negotiation
  - Multiple operational modes
    - Full- and half-duplex 100 Mbps
    - · Full- and half-duplex 10 Mbps
    - Power-saving and power-down modes
  - Highly configurable
    - Programmable MAC address
    - LED activity selection
    - Promiscuous mode support
    - CRC error-rejection control

- User-configurable interrupts
- Physical media manipulation
  - Automatic MDI/MDI-X cross-over correction
  - · Register-programmable transmit amplitude
  - Automatic polarity correction and 10BASE-T signal reception

### Analog Comparators

- Two independent integrated analog comparators
- Configurable for output to drive an output pin, generate an interrupt, or initiate an ADC sample sequence
- Compare external pin input to external pin input or to internal programmable voltage reference
- Compare a test voltage against any one of these voltages
  - · An individual external reference voltage
  - A shared single external reference voltage
  - · A shared internal reference voltage

#### Power

- On-chip Low Drop-Out (LDO) voltage regulator, with programmable output user-adjustable from 2.25 V to 2.75 V
- Low-power options on controller: Sleep and Deep-sleep modes
- Low-power options for peripherals: software controls shutdown of individual peripherals
- 3.3-V supply brown-out detection and reporting via interrupt or reset
- Flexible Reset Sources
  - Power-on reset (POR)
  - Reset pin assertion
  - Brown-out (BOR) detector alerts to system power drops
  - Software reset
  - Watchdog timer reset
  - Internal low drop-out (LDO) regulator output goes unregulated
- Industrial and extended temperature 100-pin RoHS-compliant LQFP package
- Industrial-range 108-ball RoHS-compliant BGA package

## 1.2 Target Applications

- Remote monitoring
- Electronic point-of-sale (POS) machines
- Test and measurement equipment
- Network appliances and switches
- Factory automation
- HVAC and building control
- Gaming equipment
- Motion control
- Medical instrumentation
- Fire and security
- Power and energy
- Transportation

## 1.3 High-Level Block Diagram

Figure 1-1 on page 37 depicts the features on the Stellaris LM3S6422 microcontroller.




Figure 1-1. Stellaris LM3S6422 Microcontroller High-Level Block Diagram

November 18, 2011 37

### 1.4 Functional Overview

The following sections provide an overview of the features of the LM3S6422 microcontroller. The page number in parenthesis indicates where that feature is discussed in detail. Ordering and support information can be found in "Ordering and Contact Information" on page 599.

#### 1.4.1 ARM Cortex™-M3

### 1.4.1.1 Processor Core (see page 44)

All members of the Stellaris product family, including the LM3S6422 microcontroller, are designed around an ARM Cortex™-M3 processor core. The ARM Cortex-M3 processor provides the core for a high-performance, low-cost platform that meets the needs of minimal memory implementation, reduced pin count, and low-power consumption, while delivering outstanding computational performance and exceptional system response to interrupts.

#### 1.4.1.2 Memory Map (see page 63)

A memory map lists the location of instructions and data in memory. The memory map for the LM3S6422 controller can be found in Table 2-4 on page 63. Register addresses are given as a hexadecimal increment, relative to the module's base address as shown in the memory map.

### 1.4.1.3 System Timer (SysTick) (see page 86)

Cortex-M3 includes an integrated system timer, SysTick. SysTick provides a simple, 24-bit clear-on-write, decrementing, wrap-on-zero counter with a flexible control mechanism. The counter can be used in several different ways, for example:

- An RTOS tick timer which fires at a programmable rate (for example, 100 Hz) and invokes a SysTick routine.
- A high-speed alarm timer using the system clock.
- A variable rate alarm or signal timer—the duration is range-dependent on the reference clock used and the dynamic range of the counter.
- A simple counter. Software can use this to measure time to completion and time used.
- An internal clock source control based on missing/meeting durations. The COUNTFLAG bit-field in the control and status register can be used to determine if an action completed within a set duration, as part of a dynamic clock management control loop.

#### 1.4.1.4 Nested Vectored Interrupt Controller (NVIC) (see page 87)

The LM3S6422 controller includes the ARM Nested Vectored Interrupt Controller (NVIC) on the ARM® Cortex™-M3 core. The NVIC and Cortex-M3 prioritize and handle all exceptions. All exceptions are handled in Handler Mode. The processor state is automatically stored to the stack on an exception, and automatically restored from the stack at the end of the Interrupt Service Routine (ISR). The vector is fetched in parallel to the state saving, which enables efficient interrupt entry. The processor supports tail-chaining, which enables back-to-back interrupts to be performed without the overhead of state saving and restoration. Software can set eight priority levels on 7 exceptions (system handlers) and 25 interrupts.

### 1.4.1.5 System Control Block (SCB) (see page 89)

The SCB provides system implementation information and system control, including configuration, control, and reporting of system exceptions.

### 1.4.1.6 Memory Protection Unit (MPU) (see page 89)

The MPU supports the standard ARMv7 Protected Memory System Architecture (PMSA) model. The MPU provides full support for protection regions, overlapping protection regions, access permissions, and exporting memory attributes to the system.

### 1.4.2 Motor Control Peripherals

To enhance motor control, the LM3S6422 controller features Pulse Width Modulation (PWM) outputs.

#### 1.4.2.1 PWM

Pulse width modulation (PWM) is a powerful technique for digitally encoding analog signal levels. High-resolution counters are used to generate a square wave, and the duty cycle of the square wave is modulated to encode an analog signal. Typical applications include switching power supplies and motor control.

On the LM3S6422, PWM motion control functionality can be achieved through:

■ The motion control features of the general-purpose timers using the CCP pins

#### CCP Pins (see page 303)

The General-Purpose Timer Module's CCP (Capture Compare PWM) pins are software programmable to support a simple PWM mode with a software-programmable output inversion of the PWM signal.

# 1.4.3 Analog Peripherals

To handle analog signals, the LM3S6422 microcontroller offers an Analog-to-Digital Converter (ADC).

For support of analog signals, the LM3S6422 microcontroller offers two analog comparators.

#### 1.4.3.1 ADC (see page 357)

An analog-to-digital converter (ADC) is a peripheral that converts a continuous analog voltage to a discrete digital number.

The LM3S6422 ADC module features 10-bit conversion resolution and supports two input channels, plus an internal temperature sensor. Four buffered sample sequences allow rapid sampling of up to eight analog input sources without controller intervention. Each sample sequence provides flexible programming with fully configurable input source, trigger events, interrupt generation, and sequence priority.

#### 1.4.3.2 Analog Comparators (see page 521)

An analog comparator is a peripheral that compares two analog voltages, and provides a logical output that signals the comparison result.

The LM3S6422 microcontroller provides two independent integrated analog comparators that can be configured to drive an output or generate an interrupt or ADC event.

A comparator can compare a test voltage against any one of these voltages:

An individual external reference voltage

- A shared single external reference voltage
- A shared internal reference voltage

The comparator can provide its output to a device pin, acting as a replacement for an analog comparator on the board, or it can be used to signal the application via interrupts or triggers to the ADC to cause it to start capturing a sample sequence. The interrupt generation and ADC triggering logic is separate. This means, for example, that an interrupt can be generated on a rising edge and the ADC triggered on a falling edge.

### 1.4.4 Serial Communications Peripherals

The LM3S6422 controller supports both asynchronous and synchronous serial communications with:

- One fully programmable 16C550-type UART
- One SSI module
- Ethernet controller

#### 1.4.4.1 **UART** (see page 393)

A Universal Asynchronous Receiver/Transmitter (UART) is an integrated circuit used for RS-232C serial communications, containing a transmitter (parallel-to-serial converter) and a receiver (serial-to-parallel converter), each clocked separately.

The LM3S6422 controller includes one fully programmable 16C550-type UARTthat supports data transfer speeds up to 1.5625 Mbps. (Although similar in functionality to a 16C550 UART, it is not register-compatible.) In addition, each UART is capable of supporting IrDA.

Separate 16x8 transmit (TX) and receive (RX) FIFOs reduce CPU interrupt service loading. The UART can generate individually masked interrupts from the RX, TX, modem status, and error conditions. The module provides a single combined interrupt when any of the interrupts are asserted and are unmasked.

#### 1.4.4.2 SSI (see page 435)

Synchronous Serial Interface (SSI) is a four-wire bi-directional full and low-speed communications interface.

The LM3S6422 controller includes one SSI module that provides the functionality for synchronous serial communications with peripheral devices, and can be configured to use the Freescale SPI, MICROWIRE, or TI synchronous serial interface frame formats. The size of the data frame is also configurable, and can be set between 4 and 16 bits, inclusive.

The SSI module performs serial-to-parallel conversion on data received from a peripheral device, and parallel-to-serial conversion on data transmitted to a peripheral device. The TX and RX paths are buffered with internal FIFOs, allowing up to eight 16-bit values to be stored independently.

The SSI module can be configured as either a master or slave device. As a slave device, the SSI module can also be configured to disable its output, which allows a master device to be coupled with multiple slave devices.

The SSI module also includes a programmable bit rate clock divider and prescaler to generate the output serial clock derived from the SSI module's input clock. Bit rates are generated based on the input clock and the maximum bit rate is determined by the connected peripheral.

### 1.4.4.3 Ethernet Controller (see page 473)

Ethernet is a frame-based computer networking technology for local area networks (LANs). Ethernet has been standardized as IEEE 802.3. It defines a number of wiring and signaling standards for the physical layer, two means of network access at the Media Access Control (MAC)/Data Link Layer, and a common addressing format.

The Stellaris® Ethernet Controller consists of a fully integrated media access controller (MAC) and network physical (PHY) interface device. The Ethernet Controller conforms to IEEE 802.3 specifications and fully supports 10BASE-T and 100BASE-TX standards. In addition, the Ethernet Controller supports automatic MDI/MDI-X cross-over correction.

### 1.4.5 System Peripherals

# 1.4.5.1 Programmable GPIOs (see page 251)

General-purpose input/output (GPIO) pins offer flexibility for a variety of connections.

The Stellaris GPIO module is comprised of seven physical GPIO blocks, each corresponding to an individual GPIO port. The GPIO module is FiRM-compliant (compliant to the ARM Foundation IP for Real-Time Microcontrollers specification) and supports 12-34 programmable input/output pins. The number of GPIOs available depends on the peripherals being used (see "Signal Tables" on page 535 for the signals available to each GPIO pin).

The GPIO module features programmable interrupt generation as either edge-triggered or level-sensitive on all pins, programmable control for GPIO pad configuration, and bit masking in both read and write operations through address lines. Pins configured as digital inputs are Schmitt-triggered.

#### 1.4.5.2 Three Programmable Timers (see page 297)

Programmable timers can be used to count or time external events that drive the Timer input pins.

The Stellaris General-Purpose Timer Module (GPTM) contains three GPTM blocks. Each GPTM block provides two 16-bit timers/counters that can be configured to operate independently as timers or event counters, or configured to operate as one 32-bit timer or one 32-bit Real-Time Clock (RTC). Timers can also be used to trigger analog-to-digital (ADC) conversions.

When configured in 32-bit mode, a timer can run as a Real-Time Clock (RTC), one-shot timer or periodic timer. When in 16-bit mode, a timer can run as a one-shot timer or periodic timer, and can extend its precision by using an 8-bit prescaler. A 16-bit timer can also be configured for event capture or Pulse Width Modulation (PWM) generation.

### 1.4.5.3 Watchdog Timer (see page 333)

A watchdog timer can generate an interrupt or a reset when a time-out value is reached. The watchdog timer is used to regain control when a system has failed due to a software error or to the failure of an external device to respond in the expected way.

The Stellaris Watchdog Timer module consists of a 32-bit down counter, a programmable load register, interrupt generation logic, and a locking register.

The Watchdog Timer can be configured to generate an interrupt to the controller on its first time-out, and to generate a reset signal on its second time-out. Once the Watchdog Timer has been configured, the lock register can be written to prevent the timer configuration from being inadvertently altered.

# 1.4.6 Memory Peripherals

The LM3S6422 controller offers both single-cycle SRAM and single-cycle Flash memory.

#### 1.4.6.1 SRAM (see page 225)

The LM3S6422 static random access memory (SRAM) controller supports 32 KB SRAM. The internal SRAM of the Stellaris devices starts at base address 0x2000.0000 of the device memory map. To reduce the number of time-consuming read-modify-write (RMW) operations, ARM has introduced bit-banding technology in the new Cortex-M3 processor. With a bit-band-enabled processor, certain regions in the memory map (SRAM and peripheral space) can use address aliases to access individual bits in a single, atomic operation.

### 1.4.6.2 Flash (see page 226)

The LM3S6422 Flash controller supports 96 KB of flash memory. The flash is organized as a set of 1-KB blocks that can be individually erased. Erasing a block causes the entire contents of the block to be reset to all 1s. These blocks are paired into a set of 2-KB blocks that can be individually protected. The blocks can be marked as read-only or execute-only, providing different levels of code protection. Read-only blocks cannot be erased or programmed, protecting the contents of those blocks from being modified. Execute-only blocks cannot be erased or programmed, and can only be read by the controller instruction fetch mechanism, protecting the contents of those blocks from being read by either the controller or by a debugger.

#### 1.4.7 Additional Features

### 1.4.7.1 JTAG TAP Controller (see page 150)

The Joint Test Action Group (JTAG) port is an IEEE standard that defines a Test Access Port and Boundary Scan Architecture for digital integrated circuits and provides a standardized serial interface for controlling the associated test logic. The TAP, Instruction Register (IR), and Data Registers (DR) can be used to test the interconnections of assembled printed circuit boards and obtain manufacturing information on the components. The JTAG Port also provides a means of accessing and controlling design-for-test features such as I/O pin observation and control, scan testing, and debugging.

The JTAG port is composed of the standard five pins: TRST, TCK, TMS, TDI, and TDO. Data is transmitted serially into the controller on TDI and out of the controller on TDO. The interpretation of this data is dependent on the current state of the TAP controller. For detailed information on the operation of the JTAG port and TAP controller, please refer to the IEEE Standard 1149.1-Test Access Port and Boundary-Scan Architecture.

The Stellaris JTAG controller works with the ARM JTAG controller built into the Cortex-M3 core. This is implemented by multiplexing the TDO outputs from both JTAG controllers. ARM JTAG instructions select the ARM TDO output while Stellaris JTAG instructions select the Stellaris TDO outputs. The multiplexer is controlled by the Stellaris JTAG controller, which has comprehensive programming for the ARM, Stellaris, and unimplemented JTAG instructions.

#### 1.4.7.2 System Control and Clocks (see page 163)

System control determines the overall operation of the device. It provides information about the device, controls the clocking of the device and individual peripherals, and handles reset detection and reporting.

#### 1.4.8 Hardware Details

Details on the pins and package can be found in the following sections:

- "Pin Diagram" on page 533
- "Signal Tables" on page 535
- "Operating Characteristics" on page 559
- "Electrical Characteristics" on page 560
- "Package Information" on page 601

# 2 The Cortex-M3 Processor

The ARM® Cortex<sup>™</sup>-M3 processor provides a high-performance, low-cost platform that meets the system requirements of minimal memory implementation, reduced pin count, and low power consumption, while delivering outstanding computational performance and exceptional system response to interrupts. Features include:

- Compact core.
- Thumb-2 instruction set, delivering the high-performance expected of an ARM core in the memory size usually associated with 8- and 16-bit devices; typically in the range of a few kilobytes of memory for microcontroller class applications.
- Rapid application execution through Harvard architecture characterized by separate buses for instruction and data.
- Exceptional interrupt handling, by implementing the register manipulations required for handling an interrupt in hardware.
- Deterministic, fast interrupt processing: always 12 cycles, or just 6 cycles with tail-chaining
- Memory protection unit (MPU) to provide a privileged mode of operation for complex applications.
- Migration from the ARM7<sup>™</sup> processor family for better performance and power efficiency.
- Full-featured debug solution
  - Serial Wire JTAG Debug Port (SWJ-DP)
  - Flash Patch and Breakpoint (FPB) unit for implementing breakpoints
  - Data Watchpoint and Trigger (DWT) unit for implementing watchpoints, trigger resources, and system profiling
  - Instrumentation Trace Macrocell (ITM) for support of printf style debugging
  - Trace Port Interface Unit (TPIU) for bridging to a Trace Port Analyzer
- Optimized for single-cycle flash usage
- Three sleep modes with clock gating for low power
- Single-cycle multiply instruction and hardware divide
- Atomic operations
- ARM Thumb2 mixed 16-/32-bit instruction set
- 1.25 DMIPS/MHz

The Stellaris<sup>®</sup> family of microcontrollers builds on this core to bring high-performance 32-bit computing to cost-sensitive embedded microcontroller applications, such as factory automation and control, industrial control power devices, building and home automation, and stepper motor control.

This chapter provides information on the Stellaris implementation of the Cortex-M3 processor, including the programming model, the memory model, the exception model, fault handling, and power management.

For technical details on the instruction set, see the *Cortex*™-*M3/M4 Instruction Set Technical User's Manual*.

# 2.1 Block Diagram

The Cortex-M3 processor is built on a high-performance processor core, with a 3-stage pipeline Harvard architecture, making it ideal for demanding embedded applications. The processor delivers exceptional power efficiency through an efficient instruction set and extensively optimized design, providing high-end processing hardware including a range of single-cycle and SIMD multiplication and multiply-with-accumulate capabilities, saturating arithmetic and dedicated hardware division.

To facilitate the design of cost-sensitive devices, the Cortex-M3 processor implements tightly coupled system components that reduce processor area while significantly improving interrupt handling and system debug capabilities. The Cortex-M3 processor implements a version of the Thumb® instruction set based on Thumb-2 technology, ensuring high code density and reduced program memory requirements. The Cortex-M3 instruction set provides the exceptional performance expected of a modern 32-bit architecture, with the high code density of 8-bit and 16-bit microcontrollers.

The Cortex-M3 processor closely integrates a nested interrupt controller (NVIC), to deliver industry-leading interrupt performance. The Stellaris NVIC includes a non-maskable interrupt (NMI) and provides eight interrupt priority levels. The tight integration of the processor core and NVIC provides fast execution of interrupt service routines (ISRs), dramatically reducing interrupt latency. The hardware stacking of registers and the ability to suspend load-multiple and store-multiple operations further reduce interrupt latency. Interrupt handlers do not require any assembler stubs which removes code overhead from the ISRs. Tail-chaining optimization also significantly reduces the overhead when switching from one ISR to another. To optimize low-power designs, the NVIC integrates with the sleep modes, including Deep-sleep mode, which enables the entire device to be rapidly powered down.




Figure 2-1. CPU Block Diagram

### 2.2 Overview

# 2.2.1 System-Level Interface

The Cortex-M3 processor provides multiple interfaces using AMBA® technology to provide high-speed, low-latency memory accesses. The core supports unaligned data accesses and implements atomic bit manipulation that enables faster peripheral controls, system spinlocks, and thread-safe Boolean data handling.

The Cortex-M3 processor has a memory protection unit (MPU) that provides fine-grain memory control, enabling applications to implement security privilege levels and separate code, data and stack on a task-by-task basis.

## 2.2.2 Integrated Configurable Debug

The Cortex-M3 processor implements a complete hardware debug solution, providing high system visibility of the processor and memory through either a traditional JTAG port or a 2-pin Serial Wire Debug (SWD) port that is ideal for microcontrollers and other small package devices. The Stellaris implementation replaces the ARM SW-DP and JTAG-DP with the ARM CoreSight™-compliant Serial Wire JTAG Debug Port (SWJ-DP) interface. The SWJ-DP interface combines the SWD and JTAG debug ports into one module. See the *ARM® Debug Interface V5 Architecture Specification* for details on SWJ-DP.

For system trace, the processor integrates an Instrumentation Trace Macrocell (ITM) alongside data watchpoints and a profiling unit. To enable simple and cost-effective profiling of the system trace events, a Serial Wire Viewer (SWV) can export a stream of software-generated messages, data trace, and profiling information through a single pin.

The Flash Patch and Breakpoint Unit (FPB) provides up to eight hardware breakpoint comparators that debuggers can use. The comparators in the FPB also provide remap functions of up to eight words in the program code in the CODE memory region. This enables applications stored in a read-only area of Flash memory to be patched in another area of on-chip SRAM or Flash memory. If a patch is required, the application programs the FPB to remap a number of addresses. When those addresses are accessed, the accesses are redirected to a remap table specified in the FPB configuration.

For more information on the Cortex-M3 debug capabilities, see the ARM® Debug Interface V5 Architecture Specification.

# 2.2.3 Trace Port Interface Unit (TPIU)

The TPIU acts as a bridge between the Cortex-M3 trace data from the ITM, and an off-chip Trace Port Analyzer, as shown in Figure 2-2 on page 47.

Debua Serial Wire ATB Trace Out ATB Asynchronous FIFO Trace Port Interface (serializer) Slave (SWO) Port APB APB Slave Interface Port

Figure 2-2. TPIU Block Diagram

# 2.2.4 Cortex-M3 System Component Details

The Cortex-M3 includes the following system components:

- SysTick
  - A 24-bit count-down timer that can be used as a Real-Time Operating System (RTOS) tick timer or as a simple counter (see "System Timer (SysTick)" on page 86).
- Nested Vectored Interrupt Controller (NVIC)
  - An embedded interrupt controller that supports low latency interrupt processing (see "Nested Vectored Interrupt Controller (NVIC)" on page 87).
- System Control Block (SCB)

The programming model interface to the processor. The SCB provides system implementation information and system control, including configuration, control, and reporting of system exceptions (see "System Control Block (SCB)" on page 89).

■ Memory Protection Unit (MPU)

Improves system reliability by defining the memory attributes for different memory regions. The MPU provides up to eight different regions and an optional predefined background region (see "Memory Protection Unit (MPU)" on page 89).

# 2.3 Programming Model

This section describes the Cortex-M3 programming model. In addition to the individual core register descriptions, information about the processor modes and privilege levels for software execution and stacks is included.

### 2.3.1 Processor Mode and Privilege Levels for Software Execution

The Cortex-M3 has two modes of operation:

Thread mode

Used to execute application software. The processor enters Thread mode when it comes out of reset.

■ Handler mode

Used to handle exceptions. When the processor has finished exception processing, it returns to Thread mode.

In addition, the Cortex-M3 has two privilege levels:

Unprivileged

In this mode, software has the following restrictions:

- Limited access to the MSR and MRS instructions and no use of the CPS instruction
- No access to the system timer, NVIC, or system control block
- Possibly restricted access to memory or peripherals
- Privileged

In this mode, software can use all the instructions and has access to all resources.

In Thread mode, the **CONTROL** register (see page 62) controls whether software execution is privileged or unprivileged. In Handler mode, software execution is always privileged.

Only privileged software can write to the **CONTROL** register to change the privilege level for software execution in Thread mode. Unprivileged software can use the SVC instruction to make a supervisor call to transfer control to privileged software.

#### 2.3.2 Stacks

The processor uses a full descending stack, meaning that the stack pointer indicates the last stacked item on the memory. When the processor pushes a new item onto the stack, it decrements the stack pointer and then writes the item to the new memory location. The processor implements two stacks:

the main stack and the process stack, with a pointer for each held in independent registers (see the **SP** register on page 52).

In Thread mode, the **CONTROL** register (see page 62) controls whether the processor uses the main stack or the process stack. In Handler mode, the processor always uses the main stack. The options for processor operations are shown in Table 2-1 on page 49.

Table 2-1. Summary of Processor Mode, Privilege Level, and Stack Use

Processor Mode	Use	Privilege Level	Stack Used
Thread	Applications	Privileged or unprivileged <sup>a</sup>	Main stack or process stack <sup>a</sup>
Handler	Exception handlers	Always privileged	Main stack

a. See CONTROL (page 62).

## 2.3.3 Register Map

Figure 2-3 on page 49 shows the Cortex-M3 register set. Table 2-2 on page 50 lists the Core registers. The core registers are not memory mapped and are accessed by register name, so the base address is n/a (not applicable) and there is no offset.

Figure 2-3. Cortex-M3 Register Set




Table 2-2. Processor Register Map

Offset	Name	Type	Reset	Description	See page
-	R0	R/W	-	Cortex General-Purpose Register 0	51
-	R1	R/W	-	Cortex General-Purpose Register 1	51
-	R2	R/W	-	Cortex General-Purpose Register 2	51
-	R3	R/W	-	Cortex General-Purpose Register 3	51
-	R4	R/W	-	Cortex General-Purpose Register 4	51
-	R5	R/W	-	Cortex General-Purpose Register 5	51
-	R6	R/W	-	Cortex General-Purpose Register 6	51
-	R7	R/W	-	Cortex General-Purpose Register 7	51
-	R8	R/W	-	Cortex General-Purpose Register 8	51
-	R9	R/W	-	Cortex General-Purpose Register 9	51
-	R10	R/W	-	Cortex General-Purpose Register 10	51
-	R11	R/W	-	Cortex General-Purpose Register 11	51
-	R12	R/W	-	Cortex General-Purpose Register 12	51
-	SP	R/W	-	Stack Pointer	52
-	LR	R/W	0xFFFF.FFFF	Link Register	53
-	PC	R/W	-	Program Counter	54
-	PSR	R/W	0x0100.0000	Program Status Register	55
-	PRIMASK	R/W	0x0000.0000	Priority Mask Register	59
-	FAULTMASK	R/W	0x0000.0000	Fault Mask Register	60
-	BASEPRI	R/W	0x0000.0000	Base Priority Mask Register	61
-	CONTROL	R/W	0x0000.0000	Control Register	62

# 2.3.4 Register Descriptions

This section lists and describes the Cortex-M3 registers, in the order shown in Figure 2-3 on page 49. The core registers are not memory mapped and are accessed by register name rather than offset.

**Note:** The register type shown in the register descriptions refers to type during program execution in Thread mode and Handler mode. Debug access can differ.

Register 1: Cortex General-Purpose Register 0 (R0)

Register 2: Cortex General-Purpose Register 1 (R1)

Register 3: Cortex General-Purpose Register 2 (R2)

Register 4: Cortex General-Purpose Register 3 (R3)

Register 5: Cortex General-Purpose Register 4 (R4)

Register 6: Cortex General-Purpose Register 5 (R5)

Register 7: Cortex General-Purpose Register 6 (R6)

Register 8: Cortex General-Purpose Register 7 (R7)

Register 9: Cortex General-Purpose Register 8 (R8)

Register 10: Cortex General-Purpose Register 9 (R9)

Register 11: Cortex General-Purpose Register 10 (R10)


Register 12: Cortex General-Purpose Register 11 (R11)

Register 13: Cortex General-Purpose Register 12 (R12)

The **Rn** registers are 32-bit general-purpose registers for data operations and can be accessed from either privileged or unprivileged mode.


#### Cortex General-Purpose Register 0 (R0)





### Register 14: Stack Pointer (SP)

The **Stack Pointer (SP)** is register R13. In Thread mode, the function of this register changes depending on the ASP bit in the **Control Register (CONTROL)** register. When the ASP bit is clear, this register is the **Main Stack Pointer (MSP)**. When the ASP bit is set, this register is the **Process Stack Pointer (PSP)**. On reset, the ASP bit is clear, and the processor loads the **MSP** with the value from address 0x0000.0000. The **MSP** can only be accessed in privileged mode; the **PSP** can be accessed in either privileged or unprivileged mode.




### Register 15: Link Register (LR)

The **Link Register (LR)** is register R14, and it stores the return information for subroutines, function calls, and exceptions. **LR** can be accessed from either privileged or unprivileged mode.

<code>EXC\_RETURN</code> is loaded into  $\bf LR$  on exception entry. See Table 2-10 on page 79 for the values and description.

#### Link Register (LR)

Type R/W, reset 0xFFFF.FFF



Bit/Field Name Type Reset Description


31:0 LINK R/W 0xFFF.FFF This field is the return address.

## **Register 16: Program Counter (PC)**

The **Program Counter (PC)** is register R15, and it contains the current program address. On reset, the processor loads the **PC** with the value of the reset vector, which is at address 0x0000.0004. Bit 0 of the reset vector is loaded into the THUMB bit of the **EPSR** at reset and must be 1. The **PC** register can be accessed in either privileged or unprivileged mode.

#### Program Counter (PC)





Bit/Field Name Type Reset Description

31:0 PC R/W - This field is the current program address.

#### Register 17: Program Status Register (PSR)

**Note:** This register is also referred to as **xPSR**.

The **Program Status Register (PSR)** has three functions, and the register bits are assigned to the different functions:

- Application Program Status Register (APSR), bits 31:27,
- Execution Program Status Register (EPSR), bits 26:24, 15:10
- Interrupt Program Status Register (IPSR), bits 5:0

The **PSR**, **IPSR**, and **EPSR** registers can only be accessed in privileged mode; the **APSR** register can be accessed in either privileged or unprivileged mode.

**APSR** contains the current state of the condition flags from previous instruction executions.

**EPSR** contains the Thumb state bit and the execution state bits for the If-Then (IT) instruction or the Interruptible-Continuable Instruction (ICI) field for an interrupted load multiple or store multiple instruction. Attempts to read the **EPSR** directly through application software using the MSR instruction always return zero. Attempts to write the **EPSR** using the MSR instruction in application software are always ignored. Fault handlers can examine the **EPSR** value in the stacked **PSR** to determine the operation that faulted (see "Exception Entry and Return" on page 77).

IPSR contains the exception type number of the current Interrupt Service Routine (ISR).

These registers can be accessed individually or as a combination of any two or all three registers, using the register name as an argument to the MSR or MRS instructions. For example, all of the registers can be read using **PSR** with the MRS instruction, or **APSR** only can be written to using **APSR** with the MSR instruction. page 55 shows the possible register combinations for the **PSR**. See the MRS and MSR instruction descriptions in the *Cortex™-M3/M4 Instruction Set Technical User's Manual* for more information about how to access the program status registers.


Table 2-3. PSR Register Combinations

Register	Туре	Combination
PSR	R/W <sup>a, b</sup>	APSR, EPSR, and IPSR
IEPSR	RO	EPSR and IPSR
IAPSR	R/W <sup>a</sup>	APSR and IPSR
EAPSR	R/W <sup>b</sup>	APSR and EPSR

- a. The processor ignores writes to the IPSR bits.
- b. Reads of the EPSR bits return zero, and the processor ignores writes to these bits.

#### Program Status Register (PSR)

Type R/W, reset 0x0100.0000



Bit/Field	Name	Type	Reset	Description
31	N	R/W	0	APSR Negative or Less Flag
				Value Description  1 The previous operation result was negative or less than.  0 The previous operation result was positive, zero, greater than, or equal.  The value of this bit is only meaningful when accessing PSR or APSR.
30	Z	R/W	0	APSR Zero Flag
				Value Description  1 The previous operation result was zero.  0 The previous operation result was non-zero.  The value of this bit is only meaningful when accessing PSR or APSR.
29	С	R/W	0	APSR Carry or Borrow Flag
				<ul> <li>Value Description</li> <li>The previous add operation resulted in a carry bit or the previous subtract operation did not result in a borrow bit.</li> <li>The previous add operation did not result in a carry bit or the previous subtract operation resulted in a borrow bit.</li> <li>The value of this bit is only meaningful when accessing PSR or APSR.</li> </ul>
28	V	R/W	0	APSR Overflow Flag
				Value Description  1 The previous operation resulted in an overflow.  0 The previous operation did not result in an overflow.  The value of this bit is only meaningful when accessing PSR or APSR.
27	Q	R/W	0	APSR DSP Overflow and Saturation Flag      Value Description         DSP Overflow or saturation has occurred.         DSP overflow or saturation has not occurred since reset or since the bit was last cleared.  The value of this bit is only meaningful when accessing PSR or APSR.
				The value of and bit is only incaming at when accessing For or AFOR.

This bit is cleared by software using an MRS instruction.

Bit/Field	Name	Туре	Reset	Description
26:25	ICI / IT	RO	0x0	EPSR ICI / IT status
				These bits, along with bits 15:10, contain the Interruptible-Continuable Instruction (ICI) field for an interrupted load multiple or store multiple instruction or the execution state bits of the IT instruction.
				When <b>EPSR</b> holds the ICI execution state, bits 26:25 are zero.
				The If-Then block contains up to four instructions following an IT instruction. Each instruction in the block is conditional. The conditions for the instructions are either all the same, or some can be the inverse of others. See the Cortex™-M3/M4 Instruction Set Technical User's Manual for more information.
				The value of this field is only meaningful when accessing <b>PSR</b> or <b>EPSR</b> .
24	THUMB	RO	1	EPSR Thumb State
				This bit indicates the Thumb state and should always be set.  The following can clear the THUMB bit:
				■ The BLX, BX and POP{PC} instructions
				■ Restoration from the stacked <b>xPSR</b> value on an exception return
				■ Bit 0 of the vector value on an exception entry or reset
				Attempting to execute instructions when this bit is clear results in a fault or lockup. See "Lockup" on page 81 for more information.
				The value of this bit is only meaningful when accessing <b>PSR</b> or <b>EPSR</b> .
23:16	reserved	RO	0x00	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
15:10	ICI / IT	RO	0x0	EPSR ICI / IT status
				These bits, along with bits 26:25, contain the Interruptible-Continuable Instruction (ICI) field for an interrupted load multiple or store multiple instruction or the execution state bits of the IT instruction.
				When an interrupt occurs during the execution of an LDM, STM, PUSH or POP instruction, the processor stops the load multiple or store multiple instruction operation temporarily and stores the next register operand in the multiple operation to bits 15:12. After servicing the interrupt, the processor returns to the register pointed to by bits 15:12 and resumes execution of the multiple load or store instruction. When <b>EPSR</b> holds the ICI execution state, bits 11:10 are zero.
				The If-Then block contains up to four instructions following a 16-bit IT instruction. Each instruction in the block is conditional. The conditions for the instructions are either all the same, or some can be the inverse of others. See the Cortex™-M3/M4 Instruction Set Technical User's Manual for more information.
				The value of this field is only meaningful when accessing <b>PSR</b> or <b>EPSR</b> .
9:6	reserved	RO	0x0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.

November 18, 2011 57

Bit/Field	Name	Туре	Reset	Description	
5:0	ISRNUM	RO	0x00	IPSR ISR N	umber
				This field co Service Rou	ntains the exception type number of the current Interrupt tine (ISR).
				Value	Description
				0x00	Thread mode
				0x01	Reserved
				0x02	NMI
				0x03	Hard fault
				0x04	Memory management fault
				0x05	Bus fault
				0x06	Usage fault
				0x07-0x0A	Reserved
				0x0B	SVCall
				0x0C	Reserved for Debug
				0x0D	Reserved
				0x0E	PendSV
				0x0F	SysTick
				0x10	Interrupt Vector 0
				0x11	Interrupt Vector 1
				0x3B	Interrupt Vector 43
				0x3C-0x3F	Reserved

See "Exception Types" on page 72 for more information.


The value of this field is only meaningful when accessing **PSR** or **IPSR**.

### Register 18: Priority Mask Register (PRIMASK)

The **PRIMASK** register prevents activation of all exceptions with programmable priority. Reset, non-maskable interrupt (NMI), and hard fault are the only exceptions with fixed priority. Exceptions should be disabled when they might impact the timing of critical tasks. This register is only accessible in privileged mode. The MSR and MRS instructions are used to access the **PRIMASK** register, and the CPS instruction may be used to change the value of the **PRIMASK** register. See the Cortex™-M3/M4 Instruction Set Technical User's Manual for more information on these instructions. For more information on exception priority levels, see "Exception Types" on page 72.

#### Priority Mask Register (PRIMASK)

Type R/W, reset 0x0000.0000



Bit/Field	Name	Type	Reset	Description
31:1	reserved	RO	0x0000.000	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
0	PRIMASK	R/W	0	Priority Mask

#### Value Description


- Prevents the activation of all exceptions with configurable priority.
- 0 No effect.

### Register 19: Fault Mask Register (FAULTMASK)

The **FAULTMASK** register prevents activation of all exceptions except for the Non-Maskable Interrupt (NMI). Exceptions should be disabled when they might impact the timing of critical tasks. This register is only accessible in privileged mode. The MSR and MRS instructions are used to access the **FAULTMASK** register, and the CPS instruction may be used to change the value of the **FAULTMASK** register. See the *Cortex™-M3/M4 Instruction Set Technical User's Manual* for more information on these instructions. For more information on exception priority levels, see "Exception Types" on page 72.

#### Fault Mask Register (FAULTMASK)

Type R/W, reset 0x0000.0000



Bit/Field	Name	Type	Reset	Description
31:1	reserved	RO	0x0000.000	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
0	FAULTMASK	R/W	0	Fault Mask

Value Description

- 1 Prevents the activation of all exceptions except for NMI.
- 0 No effect.

The processor clears the  ${\tt FAULTMASK}$  bit on exit from any exception handler except the NMI handler.

#### Register 20: Base Priority Mask Register (BASEPRI)


The **BASEPRI** register defines the minimum priority for exception processing. When **BASEPRI** is set to a nonzero value, it prevents the activation of all exceptions with the same or lower priority level as the **BASEPRI** value. Exceptions should be disabled when they might impact the timing of critical tasks. This register is only accessible in privileged mode. For more information on exception priority levels, see "Exception Types" on page 72.

### Base Priority Mask Register (BASEPRI)

Type R/W, reset 0x0000.0000

4:0

reserved



Bit/Field	Name	туре	Reset	Description
31:8	reserved	RO	0x0000.00	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
7:5	BASEPRI	R/W	0x0	Base Priority

Any exception that has a programmable priority level with the same or lower priority as the value of this field is masked. The **PRIMASK** register can be used to mask all exceptions with programmable priority levels. Higher priority exceptions have lower priority levels.

Value Description 0x0 All exceptions are unmasked. 0x1 All exceptions with priority level 1-7 are masked. 0x2 All exceptions with priority level 2-7 are masked. 0x3 All exceptions with priority level 3-7 are masked. All exceptions with priority level 4-7 are masked. 0x4 All exceptions with priority level 5-7 are masked. 0x5 All exceptions with priority level 6-7 are masked. 0x60x7 All exceptions with priority level 7 are masked.

RO 0x0 Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.

### Register 21: Control Register (CONTROL)


The **CONTROL** register controls the stack used and the privilege level for software execution when the processor is in Thread mode. This register is only accessible in privileged mode.

Handler mode always uses **MSP**, so the processor ignores explicit writes to the ASP bit of the **CONTROL** register when in Handler mode. The exception entry and return mechanisms automatically update the **CONTROL** register based on the EXC\_RETURN value (see Table 2-10 on page 79). In an OS environment, threads running in Thread mode should use the process stack and the kernel and exception handlers should use the main stack. By default, Thread mode uses **MSP**. To switch the stack pointer used in Thread mode to **PSP**, either use the MSR instruction to set the ASP bit, as detailed in the *Cortex*<sup>TM</sup>-*M3/M4 Instruction Set Technical User's Manual*, or perform an exception return to Thread mode with the appropriate EXC\_RETURN value, as shown in Table 2-10 on page 79.

**Note:** When changing the stack pointer, software must use an ISB instruction immediately after the MSR instruction, ensuring that instructions after the ISB execute use the new stack pointer. See the *Cortex*<sup>TM</sup>-*M3/M4 Instruction Set Technical User's Manual*.

### Control Register (CONTROL)

Type R/W, reset 0x0000.0000



Bit/Field	Name	Туре	Reset	Description
31:2	reserved	RO	0x0000.000	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
1	ASP	R/W	0	Active Stack Pointer
				Value Description
				1 <b>PSP</b> is the current stack pointer.
				0 MSP is the current stack pointer
				In Handler mode, this bit reads as zero and ignores writes. The Cortex-M3 updates this bit automatically on exception return.
0	TMPL	R/W	0	Thread Mode Privilege Level
				Value Description

Value Description

- 1 Unprivileged software can be executed in Thread mode.
- Only privileged software can be executed in Thread mode.

# 2.3.5 Exceptions and Interrupts

The Cortex-M3 processor supports interrupts and system exceptions. The processor and the Nested Vectored Interrupt Controller (NVIC) prioritize and handle all exceptions. An exception changes the normal flow of software control. The processor uses Handler mode to handle all exceptions except for reset. See "Exception Entry and Return" on page 77 for more information.

The NVIC registers control interrupt handling. See "Nested Vectored Interrupt Controller (NVIC)" on page 87 for more information.

## 2.3.6 Data Types

The Cortex-M3 supports 32-bit words, 16-bit halfwords, and 8-bit bytes. The processor also supports 64-bit data transfer instructions. All instruction and data memory accesses are little endian. See "Memory Regions, Types and Attributes" on page 64 for more information.

# 2.4 Memory Model

This section describes the processor memory map, the behavior of memory accesses, and the bit-banding features. The processor has a fixed memory map that provides up to 4 GB of addressable memory.

The memory map for the LM3S6422 controller is provided in Table 2-4 on page 63. In this manual, register addresses are given as a hexadecimal increment, relative to the module's base address as shown in the memory map.

The regions for SRAM and peripherals include bit-band regions. Bit-banding provides atomic operations to bit data (see "Bit-Banding" on page 67).

The processor reserves regions of the Private peripheral bus (PPB) address range for core peripheral registers (see "Cortex-M3 Peripherals" on page 86).

Note: Within the memory map, all reserved space returns a bus fault when read or written.

Table 2-4. Memory Map

Start	End	Description	For details, see page
Memory			
0x0000.0000	0x0001.7FFF	On-chip Flash	226
0x0001.8000	0x1FFF.FFFF	Reserved	-
0x2000.0000	0x2000.7FFF	Bit-banded on-chip SRAM	225
0x2000.8000	0x21FF.FFFF	Reserved	-
0x2200.0000	0x220F.FFFF	Bit-band alias of bit-banded on-chip SRAM starting at 0x2000.0000	225
0x2210.0000	0x3FFF.FFFF	Reserved	-
FiRM Peripherals	•	·	
0x4000.0000	0x4000.0FFF	Watchdog timer 0	336
0x4000.1000	0x4000.3FFF	Reserved	-
0x4000.4000	0x4000.4FFF	GPIO Port A	262
0x4000.5000	0x4000.5FFF	GPIO Port B	262
0x4000.6000	0x4000.6FFF	GPIO Port C	262
0x4000.7000	0x4000.7FFF	GPIO Port D	262
0x4000.8000	0x4000.8FFF	SSI0	447

Table 2-4. Memory Map (continued)

Start	End	Description	For details, see page
0x4000.9000	0x4000.BFFF	Reserved	-
0x4000.C000	0x4000.CFFF	UART0	401
0x4000.D000	0x4001.FFFF	Reserved	-
Peripherals	<u>'</u>		
0x4002.0000	0x4002.3FFF	Reserved	-
0x4002.4000	0x4002.4FFF	GPIO Port E	262
0x4002.5000	0x4002.5FFF	GPIO Port F	262
0x4002.6000	0x4002.6FFF	GPIO Port G	262
0x4002.7000	0x4002.FFFF	Reserved	-
0x4003.0000	0x4003.0FFF	Timer 0	308
0x4003.1000	0x4003.1FFF	Timer 1	308
0x4003.2000	0x4003.2FFF	Timer 2	308
0x4003.3000	0x4003.7FFF	Reserved	-
0x4003.8000	0x4003.8FFF	ADC0	366
0x4003.9000	0x4003.BFFF	Reserved	-
0x4003.C000	0x4003.CFFF	Analog Comparators	521
0x4003.D000	0x400F.CFFF	Reserved	-
0x400F.D000	0x400F.DFFF	Flash memory control	230
0x400F.E000	0x400F.EFFF	System control	176
0x400F.F000	0x41FF.FFFF	Reserved	-
0x4200.0000	0x43FF.FFFF	Bit-banded alias of 0x4000.0000 through 0x400F.FFFF	-
0x4400.0000	0xDFFF.FFFF	Reserved	-
Private Peripheral Bu	ıs	·	
0xE000.0000	0xE000.0FFF	Instrumentation Trace Macrocell (ITM)	46
0xE000.1000	0xE000.1FFF	Data Watchpoint and Trace (DWT)	46
0xE000.2000	0xE000.2FFF	Flash Patch and Breakpoint (FPB)	46
0xE000.3000	0xE000.DFFF	Reserved	-
0xE000.E000	0xE000.EFFF	Cortex-M3 Peripherals (SysTick, NVIC, MPU and SCB)	94
0xE000.F000	0xE003.FFFF	Reserved	-
0xE004.0000	0xE004.0FFF	Trace Port Interface Unit (TPIU)	47
0xE004.1000	0xFFFF.FFFF	Reserved	-

# 2.4.1 Memory Regions, Types and Attributes

The memory map and the programming of the MPU split the memory map into regions. Each region has a defined memory type, and some regions have additional memory attributes. The memory type and attributes determine the behavior of accesses to the region.

The memory types are:

- Normal: The processor can re-order transactions for efficiency and perform speculative reads.
- Device: The processor preserves transaction order relative to other transactions to Device or Strongly Ordered memory.

■ Strongly Ordered: The processor preserves transaction order relative to all other transactions.

The different ordering requirements for Device and Strongly Ordered memory mean that the memory system can buffer a write to Device memory but must not buffer a write to Strongly Ordered memory.

An additional memory attribute is Execute Never (XN), which means the processor prevents instruction accesses. A fault exception is generated only on execution of an instruction executed from an XN region.

# 2.4.2 Memory System Ordering of Memory Accesses

For most memory accesses caused by explicit memory access instructions, the memory system does not guarantee that the order in which the accesses complete matches the program order of the instructions, providing the order does not affect the behavior of the instruction sequence. Normally, if correct program execution depends on two memory accesses completing in program order, software must insert a memory barrier instruction between the memory access instructions (see "Software Ordering of Memory Accesses" on page 66).

However, the memory system does guarantee ordering of accesses to Device and Strongly Ordered memory. For two memory access instructions A1 and A2, if both A1 and A2 are accesses to either Device or Strongly Ordered memory, and if A1 occurs before A2 in program order, A1 is always observed before A2.

# 2.4.3 Behavior of Memory Accesses

Table 2-5 on page 65 shows the behavior of accesses to each region in the memory map. See "Memory Regions, Types and Attributes" on page 64 for more information on memory types and the XN attribute. Stellaris devices may have reserved memory areas within the address ranges shown below (refer to Table 2-4 on page 63 for more information).

Table 2-5. Memory Access Behavior

Address Range	Memory Region	Memory Type	Execute Never (XN)	Description
0x0000.0000 - 0x1FFF.FFF	Code	Normal	-	This executable region is for program code. Data can also be stored here.
0x2000.0000 - 0x3FFF.FFFF	SRAM	Normal	-	This executable region is for data. Code can also be stored here. This region includes bit band and bit band alias areas (see Table 2-6 on page 67).
0x4000.0000 - 0x5FFF.FFF	Peripheral	Device	XN	This region includes bit band and bit band alias areas (see Table 2-7 on page 67).
0x6000.0000 - 0x9FFF.FFFF	External RAM	Normal	-	This executable region is for data.
0xA000.0000 - 0xDFFF.FFFF	External device	Device	XN	This region is for external device memory.
0xE000.0000- 0xE00F.FFFF	Private peripheral bus	Strongly Ordered	XN	This region includes the NVIC, system timer, and system control block.
0xE010.0000- 0xFFFF.FFFF	Reserved	-	-	-

The Code, SRAM, and external RAM regions can hold programs. However, it is recommended that programs always use the Code region because the Cortex-M3 has separate buses that can perform instruction fetches and data accesses simultaneously.

The MPU can override the default memory access behavior described in this section. For more information, see "Memory Protection Unit (MPU)" on page 89.

The Cortex-M3 prefetches instructions ahead of execution and speculatively prefetches from branch target addresses.

# 2.4.4 Software Ordering of Memory Accesses

The order of instructions in the program flow does not always guarantee the order of the corresponding memory transactions for the following reasons:

- The processor can reorder some memory accesses to improve efficiency, providing this does not affect the behavior of the instruction sequence.
- The processor has multiple bus interfaces.
- Memory or devices in the memory map have different wait states.
- Some memory accesses are buffered or speculative.

"Memory System Ordering of Memory Accesses" on page 65 describes the cases where the memory system guarantees the order of memory accesses. Otherwise, if the order of memory accesses is critical, software must include memory barrier instructions to force that ordering. The Cortex-M3 has the following memory barrier instructions:

- The Data Memory Barrier (DMB) instruction ensures that outstanding memory transactions complete before subsequent memory transactions.
- The Data Synchronization Barrier (DSB) instruction ensures that outstanding memory transactions complete before subsequent instructions execute.
- The Instruction Synchronization Barrier (ISB) instruction ensures that the effect of all completed memory transactions is recognizable by subsequent instructions.

Memory barrier instructions can be used in the following situations:

- MPU programming
  - If the MPU settings are changed and the change must be effective on the very next instruction, use a DSB instruction to ensure the effect of the MPU takes place immediately at the end of context switching.
  - Use an ISB instruction to ensure the new MPU setting takes effect immediately after programming the MPU region or regions, if the MPU configuration code was accessed using a branch or call. If the MPU configuration code is entered using exception mechanisms, then an ISB instruction is not required.

#### Vector table

If the program changes an entry in the vector table and then enables the corresponding exception, use a DMB instruction between the operations. The DMB instruction ensures that if the exception is taken immediately after being enabled, the processor uses the new exception vector.

### Self-modifying code

If a program contains self-modifying code, use an ISB instruction immediately after the code modification in the program. The ISB instruction ensures subsequent instruction execution uses the updated program.

#### Memory map switching

If the system contains a memory map switching mechanism, use a  $\mbox{DSB}$  instruction after switching the memory map in the program. The  $\mbox{DSB}$  instruction ensures subsequent instruction execution uses the updated memory map.

Dynamic exception priority change

When an exception priority has to change when the exception is pending or active, use DSB instructions after the change. The change then takes effect on completion of the DSB instruction.

Memory accesses to Strongly Ordered memory, such as the System Control Block, do not require the use of DMB instructions.

For more information on the memory barrier instructions, see the *Cortex*™-*M3/M4 Instruction Set Technical User's Manual*.

### 2.4.5 Bit-Banding

A bit-band region maps each word in a bit-band alias region to a single bit in the bit-band region. The bit-band regions occupy the lowest 1 MB of the SRAM and peripheral memory regions. Accesses to the 32-MB SRAM alias region map to the 1-MB SRAM bit-band region, as shown in Table 2-6 on page 67. Accesses to the 32-MB peripheral alias region map to the 1-MB peripheral bit-band region, as shown in Table 2-7 on page 67. For the specific address range of the bit-band regions, see Table 2-4 on page 63.

**Note:** A word access to the SRAM or the peripheral bit-band alias region maps to a single bit in the SRAM or peripheral bit-band region.

A word access to a bit band address results in a word access to the underlying memory, and similarly for halfword and byte accesses. This allows bit band accesses to match the access requirements of the underlying peripheral.

Table 2-6. SRAM Memory Bit-Banding Regions

Address Range	Memory Region	Instruction and Data Accesses
0x2000.0000 - 0x200F.FFFF	SRAM bit-band region	Direct accesses to this memory range behave as SRAM memory accesses, but this region is also bit addressable through bit-band alias.
0x2200.0000 - 0x23FF.FFFF	SRAM bit-band alias	Data accesses to this region are remapped to bit band region. A write operation is performed as read-modify-write. Instruction accesses are not remapped.

Table 2-7. Peripheral Memory Bit-Banding Regions

Address Range	Memory Region	Instruction and Data Accesses
0x4000.0000 - 0x400F.FFFF	Peripheral bit-band region	Direct accesses to this memory range behave as peripheral memory accesses, but this region is also bit addressable through bit-band alias.
0x4200.0000 - 0x43FF.FFFF Peripheral bit-band alias		Data accesses to this region are remapped to bit band region. A write operation is performed as read-modify-write. Instruction accesses are not permitted.

The following formula shows how the alias region maps onto the bit-band region:

bit word offset = (byte offset 
$$x$$
 32) + (bit number  $x$  4)

```
bit_word_addr = bit_band_base + bit_word_offset
```

where:

#### bit word offset

The position of the target bit in the bit-band memory region.

#### bit word addr

The address of the word in the alias memory region that maps to the targeted bit.

#### bit band base

The starting address of the alias region.

#### byte offset

The number of the byte in the bit-band region that contains the targeted bit.

#### bit number

The bit position, 0-7, of the targeted bit.

Figure 2-4 on page 69 shows examples of bit-band mapping between the SRAM bit-band alias region and the SRAM bit-band region:

■ The alias word at 0x23FF.FFE0 maps to bit 0 of the bit-band byte at 0x200F.FFFF:

```
0x23FF.FFE0 = 0x2200.0000 + (0x000F.FFFF*32) + (0*4)
```

■ The alias word at 0x23FF.FFFC maps to bit 7 of the bit-band byte at 0x200F.FFFF:

```
0x23FF.FFFC = 0x2200.0000 + (0x000F.FFFF*32) + (7*4)
```

■ The alias word at 0x2200.0000 maps to bit 0 of the bit-band byte at 0x2000.0000:

```
0x2200.0000 = 0x2200.0000 + (0*32) + (0*4)
```

■ The alias word at 0x2200.001C maps to bit 7 of the bit-band byte at 0x2000.0000:

```
0x2200.001C = 0x2200.0000+ (0*32) + (7*4)
```

32-MB Alias Region 0x23FF.FFFC 0x23FF.FFF8 0x23FF.FFF4 0x23FF.FFF0 0x23FF.FFEC 0x23FF.FFE8 0x23FF.FFE4 0x23FF.FFE0 0x2200.0014 0x2200.000e 0x2200.0008 0x2200.001C 0x2200.0010 0x2200.0004 0x2200.0000 1-MB SRAM Bit-Band Region 3 6 5 4 3 2 0 7 0x200F.FFFE 0x200F.FFFD 0x200F.FFFF 0x200F.FFFC 5 4 3 2 1 0 4 3 0x2000.0001 0x2000.0000 0x2000.0003 0x2000.0002

Figure 2-4. Bit-Band Mapping

### 2.4.5.1 Directly Accessing an Alias Region

Writing to a word in the alias region updates a single bit in the bit-band region.

Bit 0 of the value written to a word in the alias region determines the value written to the targeted bit in the bit-band region. Writing a value with bit 0 set writes a 1 to the bit-band bit, and writing a value with bit 0 clear writes a 0 to the bit-band bit.

Bits 31:1 of the alias word have no effect on the bit-band bit. Writing 0x01 has the same effect as writing 0xFF. Writing 0x00 has the same effect as writing 0x0E.

When reading a word in the alias region, 0x0000.0000 indicates that the targeted bit in the bit-band region is clear and 0x0000.0001 indicates that the targeted bit in the bit-band region is set.


#### 2.4.5.2 Directly Accessing a Bit-Band Region

"Behavior of Memory Accesses" on page 65 describes the behavior of direct byte, halfword, or word accesses to the bit-band regions.

## 2.4.6 Data Storage

The processor views memory as a linear collection of bytes numbered in ascending order from zero. For example, bytes 0-3 hold the first stored word, and bytes 4-7 hold the second stored word. Data is stored in little-endian format, with the least-significant byte (Isbyte) of a word stored at the lowest-numbered byte, and the most-significant byte (msbyte) stored at the highest-numbered byte. Figure 2-5 on page 70 illustrates how data is stored.

Figure 2-5. Data Storage



## 2.4.7 Synchronization Primitives

The Cortex-M3 instruction set includes pairs of synchronization primitives which provide a non-blocking mechanism that a thread or process can use to obtain exclusive access to a memory location. Software can use these primitives to perform a guaranteed read-modify-write memory update sequence or for a semaphore mechanism.

A pair of synchronization primitives consists of:

- A Load-Exclusive instruction, which is used to read the value of a memory location and requests exclusive access to that location.
- A Store-Exclusive instruction, which is used to attempt to write to the same memory location and returns a status bit to a register. If this status bit is clear, it indicates that the thread or process gained exclusive access to the memory and the write succeeds; if this status bit is set, it indicates that the thread or process did not gain exclusive access to the memory and no write was performed.

The pairs of Load-Exclusive and Store-Exclusive instructions are:

- The word instructions LDREX and STREX
- The halfword instructions LDREXH and STREXH
- The byte instructions LDREXB and STREXB

Software must use a Load-Exclusive instruction with the corresponding Store-Exclusive instruction.

To perform an exclusive read-modify-write of a memory location, software must:

- 1. Use a Load-Exclusive instruction to read the value of the location.
- **2.** Modify the value, as required.
- **3.** Use a Store-Exclusive instruction to attempt to write the new value back to the memory location.
- 4. Test the returned status bit.

If the status bit is clear, the read-modify-write completed successfully. If the status bit is set, no write was performed, which indicates that the value returned at step 1 might be out of date. The software must retry the entire read-modify-write sequence.

Software can use the synchronization primitives to implement a semaphore as follows:

- **1.** Use a Load-Exclusive instruction to read from the semaphore address to check whether the semaphore is free.
- 2. If the semaphore is free, use a Store-Exclusive to write the claim value to the semaphore address.
- **3.** If the returned status bit from step 2 indicates that the Store-Exclusive succeeded, then the software has claimed the semaphore. However, if the Store-Exclusive failed, another process might have claimed the semaphore after the software performed step 1.

The Cortex-M3 includes an exclusive access monitor that tags the fact that the processor has executed a Load-Exclusive instruction. The processor removes its exclusive access tag if:

- It executes a CLREX instruction.
- It executes a Store-Exclusive instruction, regardless of whether the write succeeds.
- An exception occurs, which means the processor can resolve semaphore conflicts between different threads.

For more information about the synchronization primitive instructions, see the *Cortex™-M3/M4 Instruction Set Technical User's Manual.* 

# 2.5 Exception Model

The ARM Cortex-M3 processor and the Nested Vectored Interrupt Controller (NVIC) prioritize and handle all exceptions in Handler Mode. The processor state is automatically stored to the stack on an exception and automatically restored from the stack at the end of the Interrupt Service Routine (ISR). The vector is fetched in parallel to the state saving, enabling efficient interrupt entry. The processor supports tail-chaining, which enables back-to-back interrupts to be performed without the overhead of state saving and restoration.

Table 2-8 on page 73 lists all exception types. Software can set eight priority levels on seven of these exceptions (system handlers) as well as on 25 interrupts (listed in Table 2-9 on page 74).

Priorities on the system handlers are set with the NVIC **System Handler Priority n (SYSPRIn)** registers. Interrupts are enabled through the NVIC **Interrupt Set Enable n (ENn)** register and prioritized with the NVIC **Interrupt Priority n (PRIn)** registers. Priorities can be grouped by splitting priority levels into preemption priorities and subpriorities. All the interrupt registers are described in "Nested Vectored Interrupt Controller (NVIC)" on page 87.

Internally, the highest user-programmable priority (0) is treated as fourth priority, after a Reset, Non-Maskable Interrupt (NMI), and a Hard Fault, in that order. Note that 0 is the default priority for all the programmable priorities.

Important: After a write to clear an interrupt source, it may take several processor cycles for the NVIC to see the interrupt source de-assert. Thus if the interrupt clear is done as the last action in an interrupt handler, it is possible for the interrupt handler to complete while the NVIC sees the interrupt as still asserted, causing the interrupt handler to be re-entered errantly. This situation can be avoided by either clearing the interrupt source at the beginning of the interrupt handler or by performing a read or write after the write to clear the interrupt source (and flush the write buffer).

See "Nested Vectored Interrupt Controller (NVIC)" on page 87 for more information on exceptions and interrupts.

### 2.5.1 Exception States

Each exception is in one of the following states:

- Inactive. The exception is not active and not pending.
- **Pending.** The exception is waiting to be serviced by the processor. An interrupt request from a peripheral or from software can change the state of the corresponding interrupt to pending.
- Active. An exception that is being serviced by the processor but has not completed.

**Note:** An exception handler can interrupt the execution of another exception handler. In this case, both exceptions are in the active state.

■ **Active and Pending.** The exception is being serviced by the processor, and there is a pending exception from the same source.

## 2.5.2 Exception Types

The exception types are:

- Reset. Reset is invoked on power up or a warm reset. The exception model treats reset as a special form of exception. When reset is asserted, the operation of the processor stops, potentially at any point in an instruction. When reset is deasserted, execution restarts from the address provided by the reset entry in the vector table. Execution restarts as privileged execution in Thread mode.
- NMI. A non-maskable Interrupt (NMI) can be signaled using the NMI signal or triggered by software using the Interrupt Control and State (INTCTRL) register. This exception has the highest priority other than reset. NMI is permanently enabled and has a fixed priority of -2. NMIs cannot be masked or prevented from activation by any other exception or preempted by any exception other than reset.
- Hard Fault. A hard fault is an exception that occurs because of an error during exception processing, or because an exception cannot be managed by any other exception mechanism. Hard faults have a fixed priority of -1, meaning they have higher priority than any exception with configurable priority.
- Memory Management Fault. A memory management fault is an exception that occurs because of a memory protection related fault, including access violation and no match. The MPU or the fixed memory protection constraints determine this fault, for both instruction and data memory transactions. This fault is used to abort instruction accesses to Execute Never (XN) memory regions, even if the MPU is disabled.
- **Bus Fault.** A bus fault is an exception that occurs because of a memory-related fault for an instruction or data memory transaction such as a prefetch fault or a memory access fault. This fault can be enabled or disabled.
- **Usage Fault.** A usage fault is an exception that occurs because of a fault related to instruction execution, such as:
  - An undefined instruction
  - An illegal unaligned access
  - Invalid state on instruction execution

An error on exception return

An unaligned address on a word or halfword memory access or division by zero can cause a usage fault when the core is properly configured.

- **SVCall.** A supervisor call (SVC) is an exception that is triggered by the SVC instruction. In an OS environment, applications can use SVC instructions to access OS kernel functions and device drivers.
- **Debug Monitor.** This exception is caused by the debug monitor (when not halting). This exception is only active when enabled. This exception does not activate if it is a lower priority than the current activation.
- **PendSV.** PendSV is a pendable, interrupt-driven request for system-level service. In an OS environment, use PendSV for context switching when no other exception is active. PendSV is triggered using the **Interrupt Control and State (INTCTRL)** register.
- SysTick. A SysTick exception is an exception that the system timer generates when it reaches zero when it is enabled to generate an interrupt. Software can also generate a SysTick exception using the Interrupt Control and State (INTCTRL) register. In an OS environment, the processor can use this exception as system tick.
- Interrupt (IRQ). An interrupt, or IRQ, is an exception signaled by a peripheral or generated by a software request and fed through the NVIC (prioritized). All interrupts are asynchronous to instruction execution. In the system, peripherals use interrupts to communicate with the processor. Table 2-9 on page 74 lists the interrupts on the LM3S6422 controller.

For an asynchronous exception, other than reset, the processor can execute another instruction between when the exception is triggered and when the processor enters the exception handler.

Privileged software can disable the exceptions that Table 2-8 on page 73 shows as having configurable priority (see the **SYSHNDCTRL** register on page 128 and the **DIS0** register on page 103).

For more information about hard faults, memory management faults, bus faults, and usage faults, see "Fault Handling" on page 79.

Table 2-8. Exception Types

Exception Type	Vector Number	Priority <sup>a</sup>	Vector Address or Offset <sup>b</sup>	Activation
-	0	-	0x0000.0000	Stack top is loaded from the first entry of the vector table on reset.
Reset	1	-3 (highest)	0x0000.0004	Asynchronous
Non-Maskable Interrupt (NMI)	2	-2	0x0000.0008	Asynchronous
Hard Fault	3	-1	0x0000.000C	-
Memory Management	4	programmable <sup>c</sup>	0x0000.0010	Synchronous
Bus Fault	5	programmable <sup>c</sup>	0x0000.0014	Synchronous when precise and asynchronous when imprecise
Usage Fault	6	programmable <sup>c</sup>	0x0000.0018	Synchronous
-	7-10	-	-	Reserved
SVCall	11	programmable <sup>c</sup>	0x0000.002C	Synchronous
Debug Monitor	12	programmable <sup>c</sup>	0x0000.0030	Synchronous
-	13	-	-	Reserved

Table 2-8. Exception Types (continued)

Exception Type	Vector Number	Priority <sup>a</sup>	Vector Address or Offset <sup>b</sup>	Activation
PendSV	14	programmable <sup>c</sup>	0x0000.0038	Asynchronous
SysTick	15	programmable <sup>c</sup>	0x0000.003C	Asynchronous
Interrupts	16 and above	programmable <sup>d</sup>	0x0000.0040 and above	Asynchronous

a. 0 is the default priority for all the programmable priorities.

Table 2-9. Interrupts

Vector Number	Interrupt Number (Bit in Interrupt Registers)	Vector Address or Offset	Description
0-15	-	0x0000.0000 - 0x0000.003C	Processor exceptions
16	0	0x0000.0040	GPIO Port A
17	1	0x0000.0044	GPIO Port B
18	2	0x0000.0048	GPIO Port C
19	3	0x0000.004C	GPIO Port D
20	4	0x0000.0050	GPIO Port E
21	5	0x0000.0054	UART0
22	6	-	Reserved
23	7	0x0000.005C	SSI0
24-29	8-13	-	Reserved
30	14	0x0000.0078	ADC0 Sequence 0
31	15	0x0000.007C	ADC0 Sequence 1
32	16	0x0000.0080	ADC0 Sequence 2
33	17	0x0000.0084	ADC0 Sequence 3
34	18	0x0000.0088	Watchdog Timer 0
35	19	0x0000.008C	Timer 0A
36	20	0x0000.0090	Timer 0B
37	21	0x0000.0094	Timer 1A
38	22	0x0000.0098	Timer 1B
39	23	0x0000.009C	Timer 2A
40	24	0x0000.00A0	Timer 2B
41	25	0x0000.00A4	Analog Comparator 0
42	26	0x0000.00A8	Analog Comparator 1
43	27	-	Reserved
44	28	0x0000.00B0	System Control
45	29	0x0000.00B4	Flash Memory Control
46	30	0x0000.00B8	GPIO Port F
47	31	0x0000.00BC	GPIO Port G
48-57	32-41	-	Reserved
58	42	0x0000.00E8	Ethernet Controller

b. See "Vector Table" on page 75.

c. See SYSPRI1 on page 125.

d. See **PRIn** registers on page 111.

Table 2-9. Interrupts (continued)

	Interrupt Number (Bit in Interrupt Registers)		Description
59	43	-	Reserved

## 2.5.3 Exception Handlers

The processor handles exceptions using:

- Interrupt Service Routines (ISRs). Interrupts (IRQx) are the exceptions handled by ISRs.
- Fault Handlers. Hard fault, memory management fault, usage fault, and bus fault are fault exceptions handled by the fault handlers.
- **System Handlers.** NMI, PendSV, SVCall, SysTick, and the fault exceptions are all system exceptions that are handled by system handlers.

#### 2.5.4 Vector Table

The vector table contains the reset value of the stack pointer and the start addresses, also called exception vectors, for all exception handlers. The vector table is constructed using the vector address or offset shown in Table 2-8 on page 73. Figure 2-6 on page 76 shows the order of the exception vectors in the vector table. The least-significant bit of each vector must be 1, indicating that the exception handler is Thumb code

Figure 2-6. Vector Table

Exception number	IRQ number	Offset	Vector
59	43	0x00EC	IRQ43
18 17 16 15 14 13 12 11 10 9 8 7	2 1 0 -1 -2	0x004C 0x004C 0x0048 0x0044 0x0040 0x003C 0x003B	IRQ2 IRQ1 IRQ0 Systick PendSV Reserved Reserved for Debug SVCall
6	-10	0x0018	Usage fault
5	-11	0x0010	Bus fault
4	-12	0x0014	Memory management fault
3	-13	0x000C	Hard fault
2	-14	0x0008	NMI
1		0x0004	Reset
			Initial SP value
		0x0000	miliar or value

On system reset, the vector table is fixed at address 0x0000.0000. Privileged software can write to the **Vector Table Offset (VTABLE)** register to relocate the vector table start address to a different memory location, in the range 0x0000.0100 to 0x3FFF.FF00 (see "Vector Table" on page 75). Note that when configuring the **VTABLE** register, the offset must be aligned on a 256-byte boundary.

### 2.5.5 Exception Priorities

As Table 2-8 on page 73 shows, all exceptions have an associated priority, with a lower priority value indicating a higher priority and configurable priorities for all exceptions except Reset, Hard fault, and NMI. If software does not configure any priorities, then all exceptions with a configurable priority have a priority of 0. For information about configuring exception priorities, see page 125 and page 111.

**Note:** Configurable priority values for the Stellaris implementation are in the range 0-7. This means that the Reset, Hard fault, and NMI exceptions, with fixed negative priority values, always have higher priority than any other exception.

For example, assigning a higher priority value to IRQ[0] and a lower priority value to IRQ[1] means that IRQ[1] has higher priority than IRQ[0]. If both IRQ[1] and IRQ[0] are asserted, IRQ[1] is processed before IRQ[0].

If multiple pending exceptions have the same priority, the pending exception with the lowest exception number takes precedence. For example, if both IRQ[0] and IRQ[1] are pending and have the same priority, then IRQ[0] is processed before IRQ[1].

When the processor is executing an exception handler, the exception handler is preempted if a higher priority exception occurs. If an exception occurs with the same priority as the exception being handled, the handler is not preempted, irrespective of the exception number. However, the status of the new interrupt changes to pending.

## 2.5.6 Interrupt Priority Grouping

To increase priority control in systems with interrupts, the NVIC supports priority grouping. This grouping divides each interrupt priority register entry into two fields:

- An upper field that defines the group priority
- A lower field that defines a subpriority within the group

Only the group priority determines preemption of interrupt exceptions. When the processor is executing an interrupt exception handler, another interrupt with the same group priority as the interrupt being handled does not preempt the handler.

If multiple pending interrupts have the same group priority, the subpriority field determines the order in which they are processed. If multiple pending interrupts have the same group priority and subpriority, the interrupt with the lowest IRQ number is processed first.

For information about splitting the interrupt priority fields into group priority and subpriority, see page 119.

## 2.5.7 Exception Entry and Return

Descriptions of exception handling use the following terms:

- **Preemption.** When the processor is executing an exception handler, an exception can preempt the exception handler if its priority is higher than the priority of the exception being handled. See "Interrupt Priority Grouping" on page 77 for more information about preemption by an interrupt. When one exception preempts another, the exceptions are called nested exceptions. See "Exception Entry" on page 78 more information.
- **Return.** Return occurs when the exception handler is completed, and there is no pending exception with sufficient priority to be serviced and the completed exception handler was not handling a late-arriving exception. The processor pops the stack and restores the processor state to the state it had before the interrupt occurred. See "Exception Return" on page 79 for more information.
- **Tail-Chaining.** This mechanism speeds up exception servicing. On completion of an exception handler, if there is a pending exception that meets the requirements for exception entry, the stack pop is skipped and control transfers to the new exception handler.
- Late-Arriving. This mechanism speeds up preemption. If a higher priority exception occurs during state saving for a previous exception, the processor switches to handle the higher priority exception and initiates the vector fetch for that exception. State saving is not affected by late arrival because the state saved is the same for both exceptions. Therefore, the state saving continues uninterrupted. The processor can accept a late arriving exception until the first instruction of the exception handler of the original exception enters the execute stage of the processor. On

return from the exception handler of the late-arriving exception, the normal tail-chaining rules apply.

### 2.5.7.1 Exception Entry

Exception entry occurs when there is a pending exception with sufficient priority and either the processor is in Thread mode or the new exception is of higher priority than the exception being handled, in which case the new exception preempts the original exception.

When one exception preempts another, the exceptions are nested.

Sufficient priority means the exception has more priority than any limits set by the mask registers (see **PRIMASK** on page 59, **FAULTMASK** on page 60, and **BASEPRI** on page 61). An exception with less priority than this is pending but is not handled by the processor.

When the processor takes an exception, unless the exception is a tail-chained or a late-arriving exception, the processor pushes information onto the current stack. This operation is referred to as *stacking* and the structure of eight data words is referred to as *stack frame*.

Aligner

APSR

PC

LR

R12

R3

R2

R1

R0

IRQ top of stack

Figure 2-7. Exception Stack Frame

Immediately after stacking, the stack pointer indicates the lowest address in the stack frame. Unless stack alignment is disabled, the stack frame is aligned to a double-word address. If the STKALIGN bit of the **Configuration Control (CCR)** register is set, stack align adjustment is performed during stacking.

The stack frame includes the return address, which is the address of the next instruction in the interrupted program. This value is restored to the **PC** at exception return so that the interrupted program resumes.

In parallel to the stacking operation, the processor performs a vector fetch that reads the exception handler start address from the vector table. When stacking is complete, the processor starts executing the exception handler. At the same time, the processor writes an EXC\_RETURN value to the **LR**, indicating which stack pointer corresponds to the stack frame and what operation mode the processor was in before the entry occurred.

If no higher-priority exception occurs during exception entry, the processor starts executing the exception handler and automatically changes the status of the corresponding pending interrupt to active.

If another higher-priority exception occurs during exception entry, known as late arrival, the processor starts executing the exception handler for this exception and does not change the pending status of the earlier exception.

### 2.5.7.2 Exception Return

Exception return occurs when the processor is in Handler mode and executes one of the following instructions to load the EXC\_RETURN value into the **PC**:

- An LDM or POP instruction that loads the PC
- A BX instruction using any register
- An LDR instruction with the PC as the destination

EXC\_RETURN is the value loaded into the **LR** on exception entry. The exception mechanism relies on this value to detect when the processor has completed an exception handler. The lowest four bits of this value provide information on the return stack and processor mode. Table 2-10 on page 79 shows the EXC\_RETURN values with a description of the exception return behavior.

EXC\_RETURN bits 31:4 are all set. When this value is loaded into the **PC**, it indicates to the processor that the exception is complete, and the processor initiates the appropriate exception return sequence.

Table 2-10. Exception Return Behavior

EXC_RETURN[31:0]	Description
0xFFFF.FFF0	Reserved
0xFFFF.FFF1	Return to Handler mode.
	Exception return uses state from MSP.
	Execution uses MSP after return.
0xFFFF.FFF2 - 0xFFFF.FFF8	Reserved
0xFFFF.FFF9	Return to Thread mode.
	Exception return uses state from MSP.
	Execution uses MSP after return.
0xFFFF.FFFA - 0xFFFF.FFFC	Reserved
0xFFFF.FFFD	Return to Thread mode.
	Exception return uses state from PSP.
	Execution uses <b>PSP</b> after return.
0xFFFF.FFFE - 0xFFFF.FFFF	Reserved

# 2.6 Fault Handling

Faults are a subset of the exceptions (see "Exception Model" on page 71). The following conditions generate a fault:

- A bus error on an instruction fetch or vector table load or a data access.
- An internally detected error such as an undefined instruction or an attempt to change state with a BX instruction.
- Attempting to execute an instruction from a memory region marked as Non-Executable (XN).
- An MPU fault because of a privilege violation or an attempt to access an unmanaged region.

# 2.6.1 Fault Types

Table 2-11 on page 80 shows the types of fault, the handler used for the fault, the corresponding fault status register, and the register bit that indicates the fault has occurred. See page 132 for more information about the fault status registers.

Table 2-11. Faults

Fault	Handler	Fault Status Register	Bit Name
Bus error on a vector read	Hard fault	Hard Fault Status (HFAULTSTAT)	VECT
Fault escalated to a hard fault	Hard fault	Hard Fault Status (HFAULTSTAT)	FORCED
MPU or default memory mismatch on instruction access	Memory management fault	Memory Management Fault Status (MFAULTSTAT)	IERR <sup>a</sup>
MPU or default memory mismatch on data access	Memory management fault	Memory Management Fault Status (MFAULTSTAT)	DERR
MPU or default memory mismatch on exception stacking	Memory management fault	Memory Management Fault Status (MFAULTSTAT)	MSTKE
MPU or default memory mismatch on exception unstacking	Memory management fault	Memory Management Fault Status (MFAULTSTAT)	MUSTKE
Bus error during exception stacking	Bus fault	Bus Fault Status (BFAULTSTAT)	BSTKE
Bus error during exception unstacking	Bus fault	Bus Fault Status (BFAULTSTAT)	BUSTKE
Bus error during instruction prefetch	Bus fault	Bus Fault Status (BFAULTSTAT)	IBUS
Precise data bus error	Bus fault	Bus Fault Status (BFAULTSTAT)	PRECISE
Imprecise data bus error	Bus fault	Bus Fault Status (BFAULTSTAT)	IMPRE
Attempt to access a coprocessor	Usage fault	Usage Fault Status (UFAULTSTAT)	NOCP
Undefined instruction	Usage fault	Usage Fault Status (UFAULTSTAT)	UNDEF
Attempt to enter an invalid instruction set state <sup>b</sup>	Usage fault	Usage Fault Status (UFAULTSTAT)	INVSTAT
Invalid EXC_RETURN value	Usage fault	Usage Fault Status (UFAULTSTAT)	INVPC
Illegal unaligned load or store	Usage fault	Usage Fault Status (UFAULTSTAT)	UNALIGN
Divide by 0	Usage fault	Usage Fault Status (UFAULTSTAT)	DIV0

a. Occurs on an access to an XN region even if the MPU is disabled.

#### 2.6.2 Fault Escalation and Hard Faults

All fault exceptions except for hard fault have configurable exception priority (see **SYSPRI1** on page 125). Software can disable execution of the handlers for these faults (see **SYSHNDCTRL** on page 128).

Usually, the exception priority, together with the values of the exception mask registers, determines whether the processor enters the fault handler, and whether a fault handler can preempt another fault handler as described in "Exception Model" on page 71.

In some situations, a fault with configurable priority is treated as a hard fault. This process is called priority escalation, and the fault is described as *escalated to hard fault*. Escalation to hard fault occurs when:

A fault handler causes the same kind of fault as the one it is servicing. This escalation to hard fault occurs because a fault handler cannot preempt itself because it must have the same priority as the current priority level.

b. Attempting to use an instruction set other than the Thumb instruction set, or returning to a non load-store-multiple instruction with ICI continuation.

- A fault handler causes a fault with the same or lower priority as the fault it is servicing. This situation happens because the handler for the new fault cannot preempt the currently executing fault handler.
- An exception handler causes a fault for which the priority is the same as or lower than the currently executing exception.
- A fault occurs and the handler for that fault is not enabled.

If a bus fault occurs during a stack push when entering a bus fault handler, the bus fault does not escalate to a hard fault. Thus if a corrupted stack causes a fault, the fault handler executes even though the stack push for the handler failed. The fault handler operates but the stack contents are corrupted.

**Note:** Only Reset and NMI can preempt the fixed priority hard fault. A hard fault can preempt any exception other than Reset, NMI, or another hard fault.

### 2.6.3 Fault Status Registers and Fault Address Registers

The fault status registers indicate the cause of a fault. For bus faults and memory management faults, the fault address register indicates the address accessed by the operation that caused the fault, as shown in Table 2-12 on page 81.

Table 2-12. Fault Status and Fault Address Registers

Handler	Status Register Name	Address Register Name	Register Description
Hard fault	Hard Fault Status (HFAULTSTAT)	-	page 138
Memory management	Memory Management Fault Status	Memory Management Fault	page 132
fault	(MFAULTSTAT)	Address (MMADDR)	page 139
Bus fault	Bus Fault Status (BFAULTSTAT)	Bus Fault Address	page 132
		(FAULTADDR)	page 140
Usage fault	Usage Fault Status (UFAULTSTAT)	-	page 132

### 2.6.4 **Lockup**

The processor enters a lockup state if a hard fault occurs when executing the NMI or hard fault handlers. When the processor is in the lockup state, it does not execute any instructions. The processor remains in lockup state until it is reset, an NMI occurs, or it is halted by a debugger.

**Note:** If the lockup state occurs from the NMI handler, a subsequent NMI does not cause the processor to leave the lockup state.

# 2.7 Power Management

The Cortex-M3 processor sleep modes reduce power consumption:

- Sleep mode stops the processor clock.
- Deep-sleep mode stops the system clock and switches off the PLL and Flash memory.

The SLEEPDEEP bit of the **System Control (SYSCTRL)** register selects which sleep mode is used (see page 121). For more information about the behavior of the sleep modes, see "System Control" on page 174.

This section describes the mechanisms for entering sleep mode and the conditions for waking up from sleep mode, both of which apply to Sleep mode and Deep-sleep mode.

### 2.7.1 Entering Sleep Modes

This section describes the mechanisms software can use to put the processor into one of the sleep modes.

The system can generate spurious wake-up events, for example a debug operation wakes up the processor. Therefore, software must be able to put the processor back into sleep mode after such an event. A program might have an idle loop to put the processor back to sleep mode.

#### 2.7.1.1 Wait for Interrupt

The wait for interrupt instruction, WFI, causes immediate entry to sleep mode unless the wake-up condition is true (see "Wake Up from WFI or Sleep-on-Exit" on page 82). When the processor executes a WFI instruction, it stops executing instructions and enters sleep mode. See the Cortex™-M3/M4 Instruction Set Technical User's Manual for more information.

#### 2.7.1.2 Wait for Event

The wait for event instruction, WFE, causes entry to sleep mode conditional on the value of a one-bit event register. When the processor executes a WFE instruction, it checks the event register. If the register is 0, the processor stops executing instructions and enters sleep mode. If the register is 1, the processor clears the register and continues executing instructions without entering sleep mode.

If the event register is 1, the processor must not enter sleep mode on execution of a WFE instruction. Typically, this situation occurs if an SEV instruction has been executed. Software cannot access this register directly.

See the Cortex™-M3/M4 Instruction Set Technical User's Manual for more information.

### 2.7.1.3 Sleep-on-Exit

If the SLEEPEXIT bit of the **SYSCTRL** register is set, when the processor completes the execution of all exception handlers, it returns to Thread mode and immediately enters sleep mode. This mechanism can be used in applications that only require the processor to run when an exception occurs.

### 2.7.2 Wake Up from Sleep Mode

The conditions for the processor to wake up depend on the mechanism that cause it to enter sleep mode.

#### 2.7.2.1 Wake Up from WFI or Sleep-on-Exit

Normally, the processor wakes up only when the NVIC detects an exception with sufficient priority to cause exception entry. Some embedded systems might have to execute system restore tasks after the processor wakes up and before executing an interrupt handler. Entry to the interrupt handler can be delayed by setting the PRIMASK bit and clearing the FAULTMASK bit. If an interrupt arrives that is enabled and has a higher priority than current exception priority, the processor wakes up but does not execute the interrupt handler until the processor clears PRIMASK. For more information about **PRIMASK** and **FAULTMASK**, see page 59 and page 60.

### 2.7.2.2 Wake Up from WFE

The processor wakes up if it detects an exception with sufficient priority to cause exception entry.

In addition, if the SEVONPEND bit in the **SYSCTRL** register is set, any new pending interrupt triggers an event and wakes up the processor, even if the interrupt is disabled or has insufficient priority to cause exception entry. For more information about **SYSCTRL**, see page 121.

# 2.8 Instruction Set Summary

The processor implements a version of the Thumb instruction set. Table 2-13 on page 83 lists the supported instructions.

Note: In Table 2-13 on page 83:

- Angle brackets, <>, enclose alternative forms of the operand
- Braces, {}, enclose optional operands
- The Operands column is not exhaustive
- Op2 is a flexible second operand that can be either a register or a constant
- Most instructions can use an optional condition code suffix

For more information on the instructions and operands, see the instruction descriptions in the *Cortex™-M3/M4 Instruction Set Technical User's Manual*.

Table 2-13. Cortex-M3 Instruction Summary

Mnemonic	Operands	Brief Description	Flags
ADC, ADCS	{Rd,} Rn, Op2	Add with carry	N,Z,C,V
ADD, ADDS	{Rd,} Rn, Op2	Add	N,Z,C,V
ADD, ADDW	{Rd,} Rn , #imm12	Add	N,Z,C,V
ADR	Rd, label	Load PC-relative address	-
AND, ANDS	{Rd,} Rn, Op2	Logical AND	N,Z,C
ASR, ASRS	Rd, Rm, <rs #n></rs #n>	Arithmetic shift right	N,Z,C
В	label	Branch	-
BFC	Rd, #lsb, #width	Bit field clear	-
BFI	Rd, Rn, #lsb, #width	Bit field insert	-
BIC, BICS	{Rd,} Rn, Op2	Bit clear	N,Z,C
ВКРТ	#imm	Breakpoint	-
BL	label	Branch with link	-
BLX	Rm	Branch indirect with link	-
BX	Rm	Branch indirect	-
CBNZ	Rn, label	Compare and branch if non-zero	-
CBZ	Rn, label	Compare and branch if zero	-
CLREX	-	Clear exclusive	-
CLZ	Rd, Rm	Count leading zeros	-
CMN	Rn, Op2	Compare negative	N,Z,C,V
CMP	Rn, Op2	Compare	N,Z,C,V
CPSID	i	Change processor state, disable interrupts	-
CPSIE	i	Change processor state, enable interrupts	-
DMB	-	Data memory barrier	-
DSB	-	Data synchronization barrier	-

Table 2-13. Cortex-M3 Instruction Summary (continued)

Mnemonic	Operands	Brief Description	Flags
EOR, EORS	{Rd,} Rn, Op2	Exclusive OR	N,Z,C
ISB	-	Instruction synchronization barrier	-
IT	-	If-Then condition block	-
LDM	Rn{!}, reglist	Load multiple registers, increment after	-
LDMDB, LDMEA	Rn{!}, reglist	Load multiple registers, decrement before	-
LDMFD, LDMIA	Rn{!}, reglist	Load multiple registers, increment after	-
LDR	Rt, [Rn, #offset]	Load register with word	-
LDRB, LDRBT	Rt, [Rn, #offset]	Load register with byte	-
LDRD	Rt, Rt2, [Rn, #offset]	Load register with two bytes	-
LDREX	Rt, [Rn, #offset]	Load register exclusive	-
LDREXB	Rt, [Rn]	Load register exclusive with byte	-
LDREXH	Rt, [Rn]	Load register exclusive with halfword	-
LDRH, LDRHT	Rt, [Rn, #offset]	Load register with halfword	-
LDRSB, LDRSBT	Rt, [Rn, #offset]	Load register with signed byte	-
LDRSH, LDRSHT	Rt, [Rn, #offset]	Load register with signed halfword	-
LDRT	Rt, [Rn, #offset]	Load register with word	-
LSL, LSLS	Rd, Rm, <rs #n></rs #n>	Logical shift left	N,Z,C
LSR, LSRS	Rd, Rm, <rs #n></rs #n>	Logical shift right	N,Z,C
MLA	Rd, Rn, Rm, Ra	Multiply with accumulate, 32-bit result	-
MLS	Rd, Rn, Rm, Ra	Multiply and subtract, 32-bit result	-
MOV, MOVS	Rd, Op2	Move	N,Z,C
MOV, MOVW	Rd, #imm16	Move 16-bit constant	N,Z,C
MOVT	Rd, #imm16	Move top	-
MRS	Rd, spec_reg	Move from special register to general register	-
MSR	spec_reg, Rm	Move from general register to special register	N,Z,C,V
MUL, MULS	{Rd,} Rn, Rm	Multiply, 32-bit result	N,Z
MVN, MVNS	Rd, Op2	Move NOT	N,Z,C
NOP	-	No operation	-
ORN, ORNS	{Rd,} Rn, Op2	Logical OR NOT	N,Z,C
ORR, ORRS	{Rd,} Rn, Op2	Logical OR	N,Z,C
POP	reglist	Pop registers from stack	-
PUSH	reglist	Push registers onto stack	-
RBIT	Rd, Rn	Reverse bits	-
REV	Rd, Rn	Reverse byte order in a word	-
REV16	Rd, Rn	Reverse byte order in each halfword	-
REVSH	Rd, Rn	Reverse byte order in bottom halfword and sign extend	-
ROR, RORS	Rd, Rm, <rs #n></rs #n>	Rotate right	N,Z,C
RRX, RRXS	Rd, Rm	Rotate right with extend	N,Z,C

Table 2-13. Cortex-M3 Instruction Summary (continued)

Mnemonic	Operands	Brief Description	Flags
RSB, RSBS	{Rd,} Rn, Op2	Reverse subtract	N,Z,C,V
SBC, SBCS	{Rd,} Rn, Op2	Subtract with carry	N,Z,C,V
SBFX	Rd, Rn, #lsb, #width	Signed bit field extract	-
SDIV	{Rd,} Rn, Rm	Signed divide	-
SEV	-	Send event	-
SMLAL	RdLo, RdHi, Rn, Rm	Signed multiply with accumulate (32x32+64), 64-bit result	-
SMULL	RdLo, RdHi, Rn, Rm	Signed multiply (32x32), 64-bit result	-
SSAT	Rd, #n, Rm {,shift #s}	Signed saturate	Q
STM	Rn{!}, reglist	Store multiple registers, increment after	-
STMDB, STMEA	Rn{!}, reglist	Store multiple registers, decrement before	-
STMFD, STMIA	Rn{!}, reglist	Store multiple registers, increment after	-
STR	Rt, [Rn {, #offset}]	Store register word	-
STRB, STRBT	Rt, [Rn {, #offset}]	Store register byte	-
STRD	Rt, Rt2, [Rn {, #offset}]	Store register two words	-
STREX	Rt, Rt, [Rn {, #offset}]	Store register exclusive	-
STREXB	Rd, Rt, [Rn]	Store register exclusive byte	-
STREXH	Rd, Rt, [Rn]	Store register exclusive halfword	-
STRH, STRHT	Rt, [Rn {, #offset}]	Store register halfword	-
STRSB, STRSBT	Rt, [Rn {, #offset}]	Store register signed byte	-
STRSH, STRSHT	Rt, [Rn {, #offset}]	Store register signed halfword	-
STRT	Rt, [Rn {, #offset}]	Store register word	-
SUB, SUBS	{Rd,} Rn, Op2	Subtract	N,Z,C,V
SUB, SUBW	{Rd,} Rn, #imm12	Subtract 12-bit constant	N,Z,C,V
SVC	#imm	Supervisor call	-
SXTB	{Rd,} Rm {,ROR #n}	Sign extend a byte	-
SXTH	{Rd,} Rm {,ROR #n}	Sign extend a halfword	-
ГВВ	[Rn, Rm]	Table branch byte	-
ГВН	[Rn, Rm, LSL #1]	Table branch halfword	-
ΓEQ	Rn, Op2	Test equivalence	N,Z,C
rst	Rn, Op2	Test	N,Z,C
JBFX	Rd, Rn, #lsb, #width	Unsigned bit field extract	-
JDIV	{Rd,} Rn, Rm	Unsigned divide	-
JMLAL	RdLo, RdHi, Rn, Rm	Unsigned multiply with accumulate (32x32+32+32), 64-bit result	-
UMULL	RdLo, RdHi, Rn, Rm	Unsigned multiply (32x 2), 64-bit result	-
USAT	Rd, #n, Rm {,shift #s}	Unsigned Saturate	Q
JXTB	{Rd,} Rm, {,ROR #n}	Zero extend a Byte	-
JXTH	{Rd,} Rm, {,ROR #n}	Zero extend a Halfword	-
NFE	-	Wait for event	-
WFI	-	Wait for interrupt	-

# 3 Cortex-M3 Peripherals

This chapter provides information on the Stellaris<sup>®</sup> implementation of the Cortex-M3 processor peripherals, including:

■ SysTick (see page 86)

Provides a simple, 24-bit clear-on-write, decrementing, wrap-on-zero counter with a flexible control mechanism.

- Nested Vectored Interrupt Controller (NVIC) (see page 87)
  - Facilitates low-latency exception and interrupt handling
  - Controls power management
  - Implements system control registers
- System Control Block (SCB) (see page 89)

Provides system implementation information and system control, including configuration, control, and reporting of system exceptions.

■ Memory Protection Unit (MPU) (see page 89)

Supports the standard ARMv7 Protected Memory System Architecture (PMSA) model. The MPU provides full support for protection regions, overlapping protection regions, access permissions, and exporting memory attributes to the system.

Table 3-1 on page 86 shows the address map of the Private Peripheral Bus (PPB). Some peripheral register regions are split into two address regions, as indicated by two addresses listed.

Table 3-1. Core Peripheral Register Re	Regions
--	---------

Address	Core Peripheral	Description (see page)
0xE000.E010-0xE000.E01F	System Timer	86
0xE000.E100-0xE000.E4EF	Nested Vectored Interrupt Controller	87
0xE000.EF00-0xE000.EF03		
0xE000.ED00-0xE000.ED3F	System Control Block	89
0xE000.ED90-0xE000.EDB8	Memory Protection Unit	89

# 3.1 Functional Description

This chapter provides information on the Stellaris implementation of the Cortex-M3 processor peripherals: SysTick, NVIC, SCB and MPU.

# 3.1.1 System Timer (SysTick)

Cortex-M3 includes an integrated system timer, SysTick, which provides a simple, 24-bit clear-on-write, decrementing, wrap-on-zero counter with a flexible control mechanism. The counter can be used in several different ways, for example as:

- An RTOS tick timer that fires at a programmable rate (for example, 100 Hz) and invokes a SysTick routine.
- A high-speed alarm timer using the system clock.

- A variable rate alarm or signal timer—the duration is range-dependent on the reference clock used and the dynamic range of the counter.
- A simple counter used to measure time to completion and time used.
- An internal clock source control based on missing/meeting durations. The COUNT bit in the STCTRL control and status register can be used to determine if an action completed within a set duration, as part of a dynamic clock management control loop.

The timer consists of three registers:

- SysTick Control and Status (STCTRL): A control and status counter to configure its clock, enable the counter, enable the SysTick interrupt, and determine counter status.
- SysTick Reload Value (STRELOAD): The reload value for the counter, used to provide the counter's wrap value.
- SysTick Current Value (STCURRENT): The current value of the counter.

When enabled, the timer counts down on each clock from the reload value to zero, reloads (wraps) to the value in the **STRELOAD** register on the next clock edge, then decrements on subsequent clocks. Clearing the **STRELOAD** register disables the counter on the next wrap. When the counter reaches zero, the COUNT status bit is set. The COUNT bit clears on reads.

Writing to the **STCURRENT** register clears the register and the COUNT status bit. The write does not trigger the SysTick exception logic. On a read, the current value is the value of the register at the time the register is accessed.

The SysTick counter runs on the system clock. If this clock signal is stopped for low power mode, the SysTick counter stops. Ensure software uses aligned word accesses to access the SysTick registers.

**Note:** When the processor is halted for debugging, the counter does not decrement.

### 3.1.2 Nested Vectored Interrupt Controller (NVIC)

This section describes the Nested Vectored Interrupt Controller (NVIC) and the registers it uses. The NVIC supports:

- 25 interrupts.
- A programmable priority level of 0-7 for each interrupt. A higher level corresponds to a lower priority, so level 0 is the highest interrupt priority.
- Low-latency exception and interrupt handling.
- Level and pulse detection of interrupt signals.
- Dynamic reprioritization of interrupts.
- Grouping of priority values into group priority and subpriority fields.
- Interrupt tail-chaining.
- An external Non-maskable interrupt (NMI).

The processor automatically stacks its state on exception entry and unstacks this state on exception exit, with no instruction overhead, providing low latency exception handling.

### 3.1.2.1 Level-Sensitive and Pulse Interrupts

The processor supports both level-sensitive and pulse interrupts. Pulse interrupts are also described as edge-triggered interrupts.

A level-sensitive interrupt is held asserted until the peripheral deasserts the interrupt signal. Typically this happens because the ISR accesses the peripheral, causing it to clear the interrupt request. A pulse interrupt is an interrupt signal sampled synchronously on the rising edge of the processor clock. To ensure the NVIC detects the interrupt, the peripheral must assert the interrupt signal for at least one clock cycle, during which the NVIC detects the pulse and latches the interrupt.

When the processor enters the ISR, it automatically removes the pending state from the interrupt (see "Hardware and Software Control of Interrupts" on page 88 for more information). For a level-sensitive interrupt, if the signal is not deasserted before the processor returns from the ISR, the interrupt becomes pending again, and the processor must execute its ISR again. As a result, the peripheral can hold the interrupt signal asserted until it no longer needs servicing.

### 3.1.2.2 Hardware and Software Control of Interrupts

The Cortex-M3 latches all interrupts. A peripheral interrupt becomes pending for one of the following reasons:

- The NVIC detects that the interrupt signal is High and the interrupt is not active.
- The NVIC detects a rising edge on the interrupt signal.
- Software writes to the corresponding interrupt set-pending register bit, or to the **Software Trigger Interrupt (SWTRIG)** register to make a Software-Generated Interrupt pending. See the INT bit in the **PEND0** register on page 105 or **SWTRIG** on page 113.

A pending interrupt remains pending until one of the following:

- The processor enters the ISR for the interrupt, changing the state of the interrupt from pending to active. Then:
  - For a level-sensitive interrupt, when the processor returns from the ISR, the NVIC samples
    the interrupt signal. If the signal is asserted, the state of the interrupt changes to pending,
    which might cause the processor to immediately re-enter the ISR. Otherwise, the state of the
    interrupt changes to inactive.
  - For a pulse interrupt, the NVIC continues to monitor the interrupt signal, and if this is pulsed
    the state of the interrupt changes to pending and active. In this case, when the processor
    returns from the ISR the state of the interrupt changes to pending, which might cause the
    processor to immediately re-enter the ISR.
    - If the interrupt signal is not pulsed while the processor is in the ISR, when the processor returns from the ISR the state of the interrupt changes to inactive.
- Software writes to the corresponding interrupt clear-pending register bit
  - For a level-sensitive interrupt, if the interrupt signal is still asserted, the state of the interrupt does not change. Otherwise, the state of the interrupt changes to inactive.

For a pulse interrupt, the state of the interrupt changes to inactive, if the state was pending
or to active, if the state was active and pending.

## 3.1.3 System Control Block (SCB)

The System Control Block (SCB) provides system implementation information and system control, including configuration, control, and reporting of the system exceptions.

### 3.1.4 Memory Protection Unit (MPU)

This section describes the Memory protection unit (MPU). The MPU divides the memory map into a number of regions and defines the location, size, access permissions, and memory attributes of each region. The MPU supports independent attribute settings for each region, overlapping regions, and export of memory attributes to the system.

The memory attributes affect the behavior of memory accesses to the region. The Cortex-M3 MPU defines eight separate memory regions, 0-7, and a background region.

When memory regions overlap, a memory access is affected by the attributes of the region with the highest number. For example, the attributes for region 7 take precedence over the attributes of any region that overlaps region 7.

The background region has the same memory access attributes as the default memory map, but is accessible from privileged software only.

The Cortex-M3 MPU memory map is unified, meaning that instruction accesses and data accesses have the same region settings.

If a program accesses a memory location that is prohibited by the MPU, the processor generates a memory management fault, causing a fault exception and possibly causing termination of the process in an OS environment. In an OS environment, the kernel can update the MPU region setting dynamically based on the process to be executed. Typically, an embedded OS uses the MPU for memory protection.

Configuration of MPU regions is based on memory types (see "Memory Regions, Types and Attributes" on page 64 for more information).

Table 3-2 on page 89 shows the possible MPU region attributes. See the section called "MPU Configuration for a Stellaris Microcontroller" on page 93 for guidelines for programming a microcontroller implementation.

**Table 3-2. Memory Attributes Summary** 

Memory Type	Description					
Strongly Ordered	All accesses to Strongly Ordered memory occur in program order.					
Device	Memory-mapped peripherals					
Normal	Normal memory					

To avoid unexpected behavior, disable the interrupts before updating the attributes of a region that the interrupt handlers might access.

Ensure software uses aligned accesses of the correct size to access MPU registers:

- Except for the MPU Region Attribute and Size (MPUATTR) register, all MPU registers must be accessed with aligned word accesses.
- The MPUATTR register can be accessed with byte or aligned halfword or word accesses.

The processor does not support unaligned accesses to MPU registers.

When setting up the MPU, and if the MPU has previously been programmed, disable unused regions to prevent any previous region settings from affecting the new MPU setup.

### 3.1.4.1 Updating an MPU Region

To update the attributes for an MPU region, the MPU Region Number (MPUNUMBER), MPU Region Base Address (MPUBASE) and MPUATTR registers must be updated. Each register can be programmed separately or with a multiple-word write to program all of these registers. You can use the MPUBASEx and MPUATTRx aliases to program up to four regions simultaneously using an STM instruction.

#### Updating an MPU Region Using Separate Words

This example simple code configures one region:

Disable a region before writing new region settings to the MPU if you have previously enabled the region being changed. For example:

```
; R1 = region number
; R2 = size/enable
; R3 = attributes
; R4 = address
                        ; 0xE000ED98, MPU region number register
; Region Number
LDR R0,=MPUNUMBER
STR R1, [R0, #0x0]
BIC R2, R2, #1
                           ; Disable
STRH R2, [R0, #0x8]
STR R4, [R0, #0x4]
STRH R3, [R0, #0xA]
                           ; Region Size and Enable
                           ; Region Base Address
                           ; Region Attribute
ORR R2, #1
                            ; Enable
STRH R2, [R0, #0x8]
                           ; Region Size and Enable
```

Software must use memory barrier instructions:

- Before MPU setup, if there might be outstanding memory transfers, such as buffered writes, that might be affected by the change in MPU settings.
- After MPU setup, if it includes memory transfers that must use the new MPU settings.

However, memory barrier instructions are not required if the MPU setup process starts by entering an exception handler, or is followed by an exception return, because the exception entry and exception return mechanism cause memory barrier behavior.

Software does not need any memory barrier instructions during MPU setup, because it accesses the MPU through the Private Peripheral Bus (PPB), which is a Strongly Ordered memory region.

For example, if all of the memory access behavior is intended to take effect immediately after the programming sequence, then a DSB instruction and an ISB instruction should be used. A DSB is required after changing MPU settings, such as at the end of context switch. An ISB is required if the code that programs the MPU region or regions is entered using a branch or call. If the programming sequence is entered using a return from exception, or by taking an exception, then an ISB is not required.

### Updating an MPU Region Using Multi-Word Writes

The MPU can be programmed directly using multi-word writes, depending how the information is divided. Consider the following reprogramming:

```
; R1 = region number
; R2 = address
; R3 = size, attributes in one
LDR R0, =MPUNUMBER ; 0xE000ED98, MPU region number register
STR R1, [R0, #0x0] ; Region Number
STR R2, [R0, #0x4] ; Region Base Address
STR R3, [R0, #0x8] ; Region Attribute, Size and Enable
```

An STM instruction can be used to optimize this:

```
; R1 = region number
; R2 = address
; R3 = size, attributes in one
LDR R0, =MPUNUMBER ; 0xE000ED98, MPU region number register
STM R0, {R1-R3} ; Region number, address, attribute, size and enable
```

This operation can be done in two words for pre-packed information, meaning that the **MPU Region Base Address (MPUBASE)** register (see page 145) contains the required region number and has the VALID bit set. This method can be used when the data is statically packed, for example in a boot loader:

#### Subregions


Regions of 256 bytes or more are divided into eight equal-sized subregions. Set the corresponding bit in the SRD field of the **MPU Region Attribute and Size (MPUATTR)** register (see page 147) to disable a subregion. The least-significant bit of the SRD field controls the first subregion, and the most-significant bit controls the last subregion. Disabling a subregion means another region overlapping the disabled range matches instead. If no other enabled region overlaps the disabled subregion, the MPU issues a fault.

Regions of 32, 64, and 128 bytes do not support subregions. With regions of these sizes, the SRD field must be configured to  $0 \times 0.0$ , otherwise the MPU behavior is unpredictable.

#### Example of SRD Use

Two regions with the same base address overlap. Region one is 128 KB, and region two is 512 KB. To ensure the attributes from region one apply to the first 128 KB region, configure the SRD field for region two to 0x03 to disable the first two subregions, as Figure 3-1 on page 92 shows.

Figure 3-1. SRD Use Example



#### 3.1.4.2 MPU Access Permission Attributes

The access permission bits, TEX, S, C, B, AP, and XN of the **MPUATTR** register, control access to the corresponding memory region. If an access is made to an area of memory without the required permissions, then the MPU generates a permission fault.

Table 3-3 on page 92 shows the encodings for the  $\mathtt{TEX}$ ,  $\mathtt{C}$ ,  $\mathtt{B}$ , and  $\mathtt{S}$  access permission bits. All encodings are shown for completeness, however the current implementation of the Cortex-M3 does not support the concept of cacheability or shareability. Refer to the section called "MPU Configuration for a Stellaris Microcontroller" on page 93 for information on programming the MPU for Stellaris implementations.

Table 3-3. TEX, S, C, and B Bit Field Encoding

TEX	S	С	В	Memory Type	Shareability	Other Attributes
000b	x <sup>a</sup>	0	0	Strongly Ordered	Shareable	-
000	x <sup>a</sup>	0	1	Device	Shareable	-
000	0	1	0	Normal	Not shareable	
000	1	1	0	Normal	Shareable	Outer and inner write-through. No write
000	0	1	1	Normal	Not shareable	allocate.
000	1	1	1	Normal	Shareable	
001	0	0	0	Normal	Not shareable	Outer and inner
001	1	0	0	Normal	Shareable	noncacheable.
001	x <sup>a</sup>	0	1	Reserved encoding	-	-
001	x <sup>a</sup>	1	0	Reserved encoding	-	-
001	0	1	1	Normal	Not shareable	Outer and inner
001	1	1	1	Normal	Shareable	write-back. Write and read allocate.
010	x <sup>a</sup>	0	0	Device	Not shareable	Nonshared Device.
010	x <sup>a</sup>	0	1	Reserved encoding	-	-
010	x <sup>a</sup>	1	x <sup>a</sup>	Reserved encoding	-	-

Table 3-3. TEX, S, C, and B Bit Field Encoding (continued)

TEX	s	С	В	Memory Type	Shareability	Other Attributes
1BB	0	Α	Α	Normal	Not shareable	Cached memory (BB =
1BB	1	А	А	Normal	Shareable	outer policy, AA = inner policy).
						See Table 3-4 for the encoding of the AA and BB bits.

a. The MPU ignores the value of this bit.

Table 3-4 on page 93 shows the cache policy for memory attribute encodings with a TEX value in the range of 0x4-0x7.

Table 3-4. Cache Policy for Memory Attribute Encoding

Encoding, AA or BB	Corresponding Cache Policy
00	Non-cacheable
01	Write back, write and read allocate
10	Write through, no write allocate
11	Write back, no write allocate

Table 3-5 on page 93 shows the AP encodings in the **MPUATTR** register that define the access permissions for privileged and unprivileged software.

Table 3-5. AP Bit Field Encoding

AP Bit Field	Privileged Permissions	Unprivileged Permissions	Description
000	No access	No access	All accesses generate a permission fault.
001	R/W	No access	Access from privileged software only.
010	R/W	RO	Writes by unprivileged software generate a permission fault.
011	R/W	R/W	Full access.
100	Unpredictable	Unpredictable	Reserved.
101	RO	No access	Reads by privileged software only.
110	RO	RO	Read-only, by privileged or unprivileged software.
111	RO	RO	Read-only, by privileged or unprivileged software.

### MPU Configuration for a Stellaris Microcontroller

Stellaris microcontrollers have only a single processor and no caches. As a result, the MPU should be programmed as shown in Table 3-6 on page 93.

Table 3-6. Memory Region Attributes for Stellaris Microcontrollers

Memory Region	TEX	S	С	В	Memory Type and Attributes
Flash memory	000b	0	1	0	Normal memory, non-shareable, write-through
Internal SRAM	000b	1	1	0	Normal memory, shareable, write-through
External SRAM	000b	1	1	1	Normal memory, shareable, write-back, write-allocate
Peripherals	000b	1	0	1	Device memory, shareable

In current Stellaris microcontroller implementations, the shareability and cache policy attributes do not affect the system behavior. However, using these settings for the MPU regions can make the application code more portable. The values given are for typical situations.

#### 3.1.4.3 MPU Mismatch

When an access violates the MPU permissions, the processor generates a memory management fault (see "Exceptions and Interrupts" on page 63 for more information). The **MFAULTSTAT** register indicates the cause of the fault. See page 132 for more information.

# 3.2 Register Map

Table 3-7 on page 94 lists the Cortex-M3 Peripheral SysTick, NVIC, MPU and SCB registers. The offset listed is a hexadecimal increment to the register's address, relative to the Core Peripherals base address of 0xE000.E000.

**Note:** Register spaces that are not used are reserved for future or internal use. Software should not modify any reserved memory address.

**Table 3-7. Peripherals Register Map** 

Offset	Name	Туре	Reset	Description	See page							
System Timer (SysTick) Registers												
0x010	STCTRL	R/W	0x0000.0000	SysTick Control and Status Register	97							
0x014	STRELOAD	R/W	0x0000.0000	SysTick Reload Value Register	99							
0x018	STCURRENT	R/WC	0x0000.0000	SysTick Current Value Register	100							
Nested V	ectored Interrupt Control	ler (NVIC)	Registers									
0x100	EN0	R/W	0x0000.0000	Interrupt 0-31 Set Enable	101							
0x104	EN1	R/W	0x0000.0000	Interrupt 32-43 Set Enable	102							
0x180	DIS0	R/W	0x0000.0000	Interrupt 0-31 Clear Enable	103							
0x184	DIS1	R/W	0x0000.0000	Interrupt 32-43 Clear Enable	104							
0x200	PEND0	R/W	0x0000.0000	Interrupt 0-31 Set Pending	105							
0x204	PEND1	R/W	0x0000.0000	Interrupt 32-43 Set Pending	106							
0x280	UNPEND0	R/W	0x0000.0000	Interrupt 0-31 Clear Pending	107							
0x284	UNPEND1	R/W	0x0000.0000	Interrupt 32-43 Clear Pending	108							
0x300	ACTIVE0	RO	0x0000.0000	Interrupt 0-31 Active Bit	109							
0x304	ACTIVE1	RO	0x0000.0000	Interrupt 32-43 Active Bit	110							
0x400	PRI0	R/W	0x0000.0000	Interrupt 0-3 Priority	111							
0x404	PRI1	R/W	0x0000.0000	Interrupt 4-7 Priority	111							
0x408	PRI2	R/W	0x0000.0000	Interrupt 8-11 Priority	111							
0x40C	PRI3	R/W	0x0000.0000	Interrupt 12-15 Priority	111							
0x410	PRI4	R/W	0x0000.0000	Interrupt 16-19 Priority	111							

Table 3-7. Peripherals Register Map (continued)

Offset	Name	Туре	Reset	Description	See page
0x414	PRI5	R/W	0x0000.0000	Interrupt 20-23 Priority	111
0x418	PRI6	R/W	0x0000.0000	Interrupt 24-27 Priority	111
0x41C	PRI7	R/W	0x0000.0000	Interrupt 28-31 Priority	111
0x420	PRI8	R/W	0x0000.0000	Interrupt 32-35 Priority	111
0x424	PRI9	R/W	0x0000.0000	Interrupt 36-39 Priority	111
0x428	PRI10	R/W	0x0000.0000	Interrupt 40-43 Priority	111
0xF00	SWTRIG	WO	0x0000.0000	Software Trigger Interrupt	113
System C	ontrol Block (SCB) Regi	sters			
0xD00	CPUID	RO	0x411F.C231	CPU ID Base	114
0xD04	INTCTRL	R/W	0x0000.0000	Interrupt Control and State	115
0xD08	VTABLE	R/W	0x0000.0000	Vector Table Offset	118
0xD0C	APINT	R/W	0xFA05.0000	Application Interrupt and Reset Control	119
0xD10	SYSCTRL	R/W	0x0000.0000	System Control	121
0xD14	CFGCTRL	R/W	0x0000.0000	Configuration and Control	123
0xD18	SYSPRI1	R/W	0x0000.0000	System Handler Priority 1	125
0xD1C	SYSPRI2	R/W	0x0000.0000	System Handler Priority 2	126
0xD20	SYSPRI3	R/W	0x0000.0000	System Handler Priority 3	127
0xD24	SYSHNDCTRL	R/W	0x0000.0000	System Handler Control and State	128
0xD28	FAULTSTAT	R/W1C	0x0000.0000	Configurable Fault Status	132
0xD2C	HFAULTSTAT	R/W1C	0x0000.0000	Hard Fault Status	138
0xD34	MMADDR	R/W	-	Memory Management Fault Address	139
0xD38	FAULTADDR	R/W	-	Bus Fault Address	140
Memory F	Protection Unit (MPU) Re	gisters			I
0xD90	MPUTYPE	RO	0x0000.0800	MPU Type	141
0xD94	MPUCTRL	R/W	0x0000.0000	MPU Control	142
0xD98	MPUNUMBER	R/W	0x0000.0000	MPU Region Number	144
0xD9C	MPUBASE	R/W	0x0000.0000	MPU Region Base Address	145
0xDA0	MPUATTR	R/W	0x0000.0000	MPU Region Attribute and Size	147
0xDA4	MPUBASE1	R/W	0x0000.0000	MPU Region Base Address Alias 1	145
0xDA8	MPUATTR1	R/W	0x0000.0000	MPU Region Attribute and Size Alias 1	147
0xDAC	MPUBASE2	R/W	0x0000.0000	MPU Region Base Address Alias 2	145
0xDB0	MPUATTR2	R/W	0x0000.0000	MPU Region Attribute and Size Alias 2	147

Table 3-7. Peripherals Register Map (continued)

Offset	Name	Туре	Reset	Description	See page
0xDB4	MPUBASE3	R/W	0x0000.0000	MPU Region Base Address Alias 3	145
0xDB8	MPUATTR3	R/W	0x0000.0000	MPU Region Attribute and Size Alias 3	147

# 3.3 System Timer (SysTick) Register Descriptions

This section lists and describes the System Timer registers, in numerical order by address offset.

# Register 1: SysTick Control and Status Register (STCTRL), offset 0x010

**Note:** This register can only be accessed from privileged mode.

The SysTick **STCTRL** register enables the SysTick features.

SysTick Control and Status Register (STCTRL)

Base 0xE000.E000 Offset 0x010 Type R/W, reset 0x0000.0000

_	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16
	'						' '	reserved						'		COUNT
Туре	RO	RO	RO	RO 0	RO	RO 0	RO	RO	RO 0	RO	RO 0	RO	RO 0	RO 0	RO	RO
Reset	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0
	15	14	13	12	11	10	9	8	7	6	5	4	3	2	1	0
	'				•		reserved			'				CLK_SRC	INTEN	ENABLE
Type Reset	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	R/W 0	R/W 0	R/W 0
Reset	U	U	U	U	U	U	U	U	U	U	U	U	U	U	U	U
В	Bit/Field		Nam	e	Ту	ре	Reset	Des	cription							
	31:17		reserv	ed .	R	0	0x000	compatibility		oftware should not rely on the value of a reserved bit. To provide ompatibility with future products, the value of a reserved bit should be served across a read-modify-write operation.						
	16		COU	NT	R	0	0	Cou	nt Flag							
								Valu	ue	Descrip	otion					
								0			The SysTick timer has not counted to 0 since the last time this bit was read.					ast time
								1		,	sTick tim was read		ounted	to 0 since	the las	st time
									bit is cle			the regis	ter or if	the <b>STCU</b>	RRENT	register
								If read by the debugger using the DAP, this bit is cleared only if the MasterType bit in the AHB-AP Control Register is clear. Other the COUNT bit is not changed by the debugger read. See the ARM Debug Interface V5 Architecture Specification for more information MasterType.					herwise, I <i>RM</i> ®			
	15:3		reserv	ed .	R	0	0x000	Software should not rely on the value of a reserved bit. To compatibility with future products, the value of a reserved preserved across a read-modify-write operation.		•						
	2		CLK_S	RC	R/	W	0	Cloc	ck Source	е						
								Valu	ue Desc	ription						

Because an external reference clock is not implemented, this bit must be set in order for SysTick to operate.

microcontrollers.) System clock

External reference clock. (Not implemented for most Stellaris

Bit/Field	Name	Туре	Reset	Description			
1	INTEN	R/W	0	Interrupt	Enable		
				Value	Description		
				0	Interrupt generation is disabled. Software can use the COUNT bit to determine if the counter has ever reached 0.		
				1	An interrupt is generated to the NVIC when SysTick counts to 0.		
0	ENABLE	R/W	0	Enable			
				Value	Description		
				0	The counter is disabled.		
				1	Enables SysTick to operate in a multi-shot way. That is, the counter loads the RELOAD value and begins counting down. On reaching 0, the COUNT bit is set and an interrupt is generated if enabled by INTEN. The counter then loads the RELOAD value again and begins counting.		

## Register 2: SysTick Reload Value Register (STRELOAD), offset 0x014

Note: This register can only be accessed from privileged mode.


The **STRELOAD** register specifies the start value to load into the **SysTick Current Value** (**STCURRENT**) register when the counter reaches 0. The start value can be between 0x1 and 0x00FF.FFFF. A start value of 0 is possible but has no effect because the SysTick interrupt and the COUNT bit are activated when counting from 1 to 0.

SysTick can be configured as a multi-shot timer, repeated over and over, firing every N+1 clock pulses, where N is any value from 1 to 0x00FF.FFFF. For example, if a tick interrupt is required every 100 clock pulses, 99 must be written into the RELOAD field.

SysTick Reload Value Register (STRELOAD)

Base 0xE000.E000

Offset 0x014
Type R/W, reset 0x0000.0000



Bit/Field	Name	Type	Reset	Description
31:24	reserved	RO	0x00	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
23:0	RELOAD	R/W	0x00.0000	Reload Value

Value to load into the  $\mbox{\bf SysTick}$  Current Value (STCURRENT) register when the counter reaches 0.

## Register 3: SysTick Current Value Register (STCURRENT), offset 0x018


**Note:** This register can only be accessed from privileged mode.

The **STCURRENT** register contains the current value of the SysTick counter.

SysTick Current Value Register (STCURRENT)

Base 0xE000.E000 Offset 0x018

Type R/WC, reset 0x0000.0000



No read-modify-write protection is provided, so change with care. This register is write-clear. Writing to it with any value clears the register.

Clearing this register also clears the COUNT bit of the STCTRL register.

# 3.4 NVIC Register Descriptions

This section lists and describes the NVIC registers, in numerical order by address offset.

The NVIC registers can only be fully accessed from privileged mode, but interrupts can be pended while in unprivileged mode by enabling the **Configuration and Control (CFGCTRL)** register. Any other unprivileged mode access causes a bus fault.

Ensure software uses correctly aligned register accesses. The processor does not support unaligned accesses to NVIC registers.

An interrupt can enter the pending state even if it is disabled.

Before programming the **VTABLE** register to relocate the vector table, ensure the vector table entries of the new vector table are set up for fault handlers, NMI, and all enabled exceptions such as interrupts. For more information, see page 118.

# Register 4: Interrupt 0-31 Set Enable (EN0), offset 0x100

Note: This register can only be accessed from privileged mode.


The **EN0** register enables interrupts and shows which interrupts are enabled. Bit 0 corresponds to Interrupt 0; bit 31 corresponds to Interrupt 31.

See Table 2-9 on page 74 for interrupt assignments.

If a pending interrupt is enabled, the NVIC activates the interrupt based on its priority. If an interrupt is not enabled, asserting its interrupt signal changes the interrupt state to pending, but the NVIC never activates the interrupt, regardless of its priority.

#### Interrupt 0-31 Set Enable (EN0)

Base 0xE000.E000 Offset 0x100 Type R/W, reset 0x0000.0000



Bit/Field	Name	Type	Reset	Description
31:0	INT	R/W	0x0000.0000	Interrupt Enable

Value	Description
0	On a read, indicates the interrupt is disabled.
	On a write, no effect.
1	On a read, indicates the interrupt is enabled.
	On a write, enables the interrupt.

A bit can only be cleared by setting the corresponding  ${\tt INT[n]}$  bit in the DISn register.

# Register 5: Interrupt 32-43 Set Enable (EN1), offset 0x104

Note: This register can only be accessed from privileged mode.


The **EN1** register enables interrupts and shows which interrupts are enabled. Bit 0 corresponds to Interrupt 32; bit 11 corresponds to Interrupt 43. See Table 2-9 on page 74 for interrupt assignments.

If a pending interrupt is enabled, the NVIC activates the interrupt based on its priority. If an interrupt is not enabled, asserting its interrupt signal changes the interrupt state to pending, but the NVIC never activates the interrupt, regardless of its priority.

#### Interrupt 32-43 Set Enable (EN1)

Base 0xE000.E000 Offset 0x104

Type R/W, reset 0x0000.0000



Bit/Field	Name	Type	Reset	Description
31:12	reserved	RO	0x0000.0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
11:0	INT	R/W	0x000	Interrupt Enable

Value	Description
0	On a read, indicates the interrupt is disabled.
	On a write, no effect.
1	On a read, indicates the interrupt is enabled.
	On a write, enables the interrupt.

A bit can only be cleared by setting the corresponding  ${\tt INT[n]}$  bit in the **DIS1** register.

# Register 6: Interrupt 0-31 Clear Enable (DIS0), offset 0x180

Note: This register can only be accessed from privileged mode.


The **DIS0** register disables interrupts. Bit 0 corresponds to Interrupt 0; bit 31 corresponds to Interrupt 31.

See Table 2-9 on page 74 for interrupt assignments.

#### Interrupt 0-31 Clear Enable (DIS0)

Base 0xE000.E000 Offset 0x180

Type R/W, reset 0x0000.0000



Value Description

On a read, indicates the interrupt is disabled.

On a write, no effect.

On a read, indicates the interrupt is enabled.

On a write, clears the corresponding  ${\tt INT[n]}$  bit in the EN0 register, disabling interrupt [n].

# Register 7: Interrupt 32-43 Clear Enable (DIS1), offset 0x184


Note: This register can only be accessed from privileged mode.

The **DIS1** register disables interrupts. Bit 0 corresponds to Interrupt 32; bit 11 corresponds to Interrupt 43. See Table 2-9 on page 74 for interrupt assignments.

Interrupt 32-43 Clear Enable (DIS1)

Base 0xE000.E000

Offset 0x184
Type R/W, reset 0x0000.0000



Bit/Field	Name	Type	Reset	Description
31:12	reserved	RO	0x0000.0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
11:0	INT	R/W	0x000	Interrupt Disable

Value Description

- On a read, indicates the interrupt is disabled.
  - On a write, no effect.
- On a read, indicates the interrupt is enabled. On a write, clears the corresponding INT[n] bit in the EN1 register, disabling interrupt [n].

# Register 8: Interrupt 0-31 Set Pending (PEND0), offset 0x200

**Note:** This register can only be accessed from privileged mode.


The **PEND0** register forces interrupts into the pending state and shows which interrupts are pending. Bit 0 corresponds to Interrupt 0; bit 31 corresponds to Interrupt 31.

See Table 2-9 on page 74 for interrupt assignments.

#### Interrupt 0-31 Set Pending (PEND0)

Base 0xE000.E000 Offset 0x200

Type R/W, reset 0x0000.0000



Bit/Field	Name	Туре	Reset	Description
31:0	INT	R/W	0x0000.0000	Interrupt Set Pending

Value	Description
0	On a read, indicates that the interrupt is not pending.
	On a write, no effect.
1	On a read, indicates that the interrupt is pending.
	On a write, the corresponding interrupt is set to pending even if it is disabled

If the corresponding interrupt is already pending, setting a bit has no

A bit can only be cleared by setting the corresponding INT[n] bit in the **UNPEND0** register.

# Register 9: Interrupt 32-43 Set Pending (PEND1), offset 0x204


Note: This register can only be accessed from privileged mode.

The **PEND1** register forces interrupts into the pending state and shows which interrupts are pending. Bit 0 corresponds to Interrupt 32; bit 11 corresponds to Interrupt 43. See Table 2-9 on page 74 for interrupt assignments.

#### Interrupt 32-43 Set Pending (PEND1)

Base 0xE000.E000 Offset 0x204

Type R/W, reset 0x0000.0000



Bit/Field	Name	Type	Reset	Description
31:12	reserved	RO	0x0000.0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
11:0	INT	R/W	0x000	Interrupt Set Pending

Value	Description
0	On a read, indicates that the interrupt is not pending.
	On a write, no effect.
1	On a read, indicates that the interrupt is pending.
	On a write, the corresponding interrupt is set to pending even if it is disabled

If the corresponding interrupt is already pending, setting a bit has no effect.

A bit can only be cleared by setting the corresponding  ${\tt INT[n]}$  bit in the <code>UNPEND1</code> register.

## Register 10: Interrupt 0-31 Clear Pending (UNPEND0), offset 0x280

**Note:** This register can only be accessed from privileged mode.


The **UNPEND0** register shows which interrupts are pending and removes the pending state from interrupts. Bit 0 corresponds to Interrupt 0; bit 31 corresponds to Interrupt 31.

See Table 2-9 on page 74 for interrupt assignments.

#### Interrupt 0-31 Clear Pending (UNPEND0)

Base 0xE000.E000 Offset 0x280

Type R/W, reset 0x0000.0000



#### Value Description

- On a read, indicates that the interrupt is not pending. On a write, no effect.
- On a read, indicates that the interrupt is pending.

  On a write, clears the corresponding INT[n] bit in the **PEND0** register, so that interrupt [n] is no longer pending.

  Setting a bit does not affect the active state of the corresponding interrupt.

## Register 11: Interrupt 32-43 Clear Pending (UNPEND1), offset 0x284


Note: This register can only be accessed from privileged mode.

The **UNPEND1** register shows which interrupts are pending and removes the pending state from interrupts. Bit 0 corresponds to Interrupt 32; bit 11 corresponds to Interrupt 43. See Table 2-9 on page 74 for interrupt assignments.

#### Interrupt 32-43 Clear Pending (UNPEND1)

Base 0xE000.E000 Offset 0x284

Type R/W, reset 0x0000.0000



Bit/Field	Name	Type	Reset	Description
31:12	reserved	RO	0x0000.0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
11:0	INT	R/W	0x000	Interrupt Clear Pending

#### Value Description

- On a read, indicates that the interrupt is not pending.
  On a write, no effect.
- On a read, indicates that the interrupt is pending.

  On a write, clears the corresponding INT[n] bit in the **PEND1** register, so that interrupt [n] is no longer pending.

  Setting a bit does not affect the active state of the corresponding interrupt.

## Register 12: Interrupt 0-31 Active Bit (ACTIVE0), offset 0x300

Note: This register can only be accessed from privileged mode.


The ACTIVEO register indicates which interrupts are active. Bit 0 corresponds to Interrupt 0; bit 31 corresponds to Interrupt 31.

See Table 2-9 on page 74 for interrupt assignments.

### Caution – Do not manually set or clear the bits in this register.

#### Interrupt 0-31 Active Bit (ACTIVE0)

Base 0xE000.E000 Offset 0x300 Type RO, reset 0x0000.0000



Divi icia	Name	Турс	reset	Description
31:0	INT	RO	0x0000.0000	Interrupt Active

Value Description

- 0 The corresponding interrupt is not active.
- The corresponding interrupt is active, or active and pending.

## Register 13: Interrupt 32-43 Active Bit (ACTIVE1), offset 0x304


Note: This register can only be accessed from privileged mode.

The ACTIVE1 register indicates which interrupts are active. Bit 0 corresponds to Interrupt 32; bit 11 corresponds to Interrupt 43. See Table 2-9 on page 74 for interrupt assignments.

#### Caution – Do not manually set or clear the bits in this register.

#### Interrupt 32-43 Active Bit (ACTIVE1)

Base 0xE000.E000 Offset 0x304 Type RO, reset 0x0000.0000



Bit/Field	Name	Type	Reset	Description
31:12	reserved	RO	0x0000.0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
11:0	INT	RO	0x000	Interrupt Active

#### Value Description

- 0 The corresponding interrupt is not active.
- 1 The corresponding interrupt is active, or active and pending.

Register 14: Interrupt 0-3 Priority (PRI0), offset 0x400

Register 15: Interrupt 4-7 Priority (PRI1), offset 0x404

Register 16: Interrupt 8-11 Priority (PRI2), offset 0x408

Register 17: Interrupt 12-15 Priority (PRI3), offset 0x40C

Register 18: Interrupt 16-19 Priority (PRI4), offset 0x410

Register 19: Interrupt 20-23 Priority (PRI5), offset 0x414

Register 20: Interrupt 24-27 Priority (PRI6), offset 0x418

Register 21: Interrupt 28-31 Priority (PRI7), offset 0x41C

Register 22: Interrupt 32-35 Priority (PRI8), offset 0x420

Register 23: Interrupt 36-39 Priority (PRI9), offset 0x424

Register 24: Interrupt 40-43 Priority (PRI10), offset 0x428

**Note:** This register can only be accessed from privileged mode.

The **PRIn** registers provide 3-bit priority fields for each interrupt. These registers are byte accessible. Each register holds four priority fields that are assigned to interrupts as follows:

PRIn Register Bit Field	Interrupt
Bits 31:29	Interrupt [4n+3]
Bits 23:21	Interrupt [4n+2]
Bits 15:13	Interrupt [4n+1]
Bits 7:5	Interrupt [4n]

See Table 2-9 on page 74 for interrupt assignments.


Each priority level can be split into separate group priority and subpriority fields. The PRIGROUP field in the **Application Interrupt and Reset Control (APINT)** register (see page 119) indicates the position of the binary point that splits the priority and subpriority fields.

These registers can only be accessed from privileged mode.

#### Interrupt 0-3 Priority (PRI0)

Base 0xE000.E000 Offset 0x400

Type R/W, reset 0x0000.0000



Bit/Field	Name	Type	Reset	Description
31:29	INTD	R/W	0x0	Interrupt Priority for Interrupt [4n+3] This field holds a priority value, 0-7, for the interrupt with the number [4n+3], where n is the number of the <b>Interrupt Priority</b> register (n=0 for <b>PRIO</b> , and so on). The lower the value, the greater the priority of the corresponding interrupt.
28:24	reserved	RO	0x0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
23:21	INTC	R/W	0x0	Interrupt Priority for Interrupt [4n+2]
				This field holds a priority value, 0-7, for the interrupt with the number [4n+2], where n is the number of the <b>Interrupt Priority</b> register (n=0 for <b>PRIO</b> , and so on). The lower the value, the greater the priority of the corresponding interrupt.
20:16	reserved	RO	0x0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
15:13	INTB	R/W	0x0	Interrupt Priority for Interrupt [4n+1]
				This field holds a priority value, 0-7, for the interrupt with the number [4n+1], where n is the number of the <b>Interrupt Priority</b> register (n=0 for <b>PRIO</b> , and so on). The lower the value, the greater the priority of the corresponding interrupt.
12:8	reserved	RO	0x0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
7:5	INTA	R/W	0x0	Interrupt Priority for Interrupt [4n]
				This field holds a priority value, 0-7, for the interrupt with the number [4n], where n is the number of the <b>Interrupt Priority</b> register (n=0 for <b>PRIO</b> , and so on). The lower the value, the greater the priority of the corresponding interrupt.
4:0	reserved	RO	0x0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.

## Register 25: Software Trigger Interrupt (SWTRIG), offset 0xF00

Note: Only privileged software can enable unprivileged access to the SWTRIG register.


Writing an interrupt number to the **SWTRIG** register generates a Software Generated Interrupt (SGI). See Table 2-9 on page 74 for interrupt assignments.

When the MAINPEND bit in the **Configuration and Control (CFGCTRL)** register (see page 123) is set, unprivileged software can access the **SWTRIG** register.

#### Software Trigger Interrupt (SWTRIG)

Base 0xE000.E000 Offset 0xF00

Type WO, reset 0x0000.0000



Bit/Field	Name	Type	Reset	Description
31:6	reserved	RO	0x0000.00	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
5:0	INTID	WO	0x00	Interrupt ID

This field holds the interrupt ID of the required SGI. For example, a value of 0x3 generates an interrupt on IRQ3.

# 3.5 System Control Block (SCB) Register Descriptions

This section lists and describes the System Control Block (SCB) registers, in numerical order by address offset. The SCB registers can only be accessed from privileged mode.

All registers must be accessed with aligned word accesses except for the **FAULTSTAT** and **SYSPRI1-SYSPRI3** registers, which can be accessed with byte or aligned halfword or word accesses. The processor does not support unaligned accesses to system control block registers.


## Register 26: CPU ID Base (CPUID), offset 0xD00

**Note:** This register can only be accessed from privileged mode.

The **CPUID** register contains the ARM® Cortex<sup>™</sup>-M3 processor part number, version, and implementation information.

#### CPU ID Base (CPUID)

Base 0xE000.E000 Offset 0xD00 Type RO, reset 0x411F.C231



Bit/Field	Name	Туре	Reset	Description
31:24	IMP	R0	0x41	Implementer Code
				Value Description
				0x41 ARM
23:20	VAR	RO	0x1	Variant Number
				Value Description
				0x1 The rn value in the rnpn product revision identifier, for example, the 1 in r1p1.
19:16	CON	RO	0xF	Constant
				Value Description
				0xF Always reads as 0xF.
15:4	PARTNO	RO	0xC23	Part Number
				Value Description
				0xC23 Cortex-M3 processor.
3:0	REV	RO	0x1	Revision Number
				Value Description

0x1 The pn value in the rnpn product revision identifier, for example, the 1 in r1p1.

## Register 27: Interrupt Control and State (INTCTRL), offset 0xD04

Note: This register can only be accessed from privileged mode.

The **INCTRL** register provides a set-pending bit for the NMI exception, and set-pending and clear-pending bits for the PendSV and SysTick exceptions. In addition, bits in this register indicate the exception number of the exception being processed, whether there are preempted active exceptions, the exception number of the highest priority pending exception, and whether any interrupts are pending.


When writing to **INCTRL**, the effect is unpredictable when writing a 1 to both the PENDSV and UNPENDSV bits, or writing a 1 to both the PENDSTSET and PENDSTCLR bits.

#### Interrupt Control and State (INTCTRL)

Base 0xE000.E000 Offset 0xD04

28

Type R/W, reset 0x0000.0000



1

Bit/Field	Name	Type	Reset	Description
31	NMISET	R/W	0	NMI Set Pendin

#### Value Description

- On a read, indicates an NMI exception is not pending.
   On a write, no effect.
  - On a read, indicates an NMI exception is pending.

    On a write, changes the NMI exception state to pending.

Because NMI is the highest-priority exception, normally the processor enters the NMI exception handler as soon as it registers the setting of this bit, and clears this bit on entering the interrupt handler. A read of this bit by the NMI exception handler returns 1 only if the NMI signal is reasserted while the processor is executing that handler.

30:29	reserved	RO	0x0	

R/W

n

**PENDSV** 

Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.

#### PendSV Set Pending

#### Value Description

- On a read, indicates a PendSV exception is not pending.
   On a write, no effect.
- On a read, indicates a PendSV exception is pending.
   On a write, changes the PendSV exception state to pending.

Setting this bit is the only way to set the PendSV exception state to pending. This bit is cleared by writing a 1 to the  ${\tt UNPENDSV}$  bit.

Bit/Field	Name	Туре	Reset	Description
27	UNPENDSV	WO	0	PendSV Clear Pending
				Value Description
				0 On a write, no effect.
				On a write, removes the pending state from the PendSV exception.
				This bit is write only; on a register read, its value is unknown.
26	PENDSTSET	R/W	0	SysTick Set Pending
				Value Description
				<ul> <li>On a read, indicates a SysTick exception is not pending.</li> <li>On a write, no effect.</li> </ul>
				1 On a read, indicates a SysTick exception is pending.
				On a write, changes the SysTick exception state to pending.
				This bit is cleared by writing a 1 to the PENDSTCLR bit.
25	PENDSTCLR	WO	0	SysTick Clear Pending
				Value Description
				0 On a write, no effect.
				On a write, removes the pending state from the SysTick exception.
				This bit is write only; on a register read, its value is unknown.
24	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
23	ISRPRE	RO	0	Debug Interrupt Handling
				Value Description
				0 The release from halt does not take an interrupt.
				1 The release from halt takes an interrupt.
				This bit is only meaningful in Debug mode and reads as zero when the processor is not in Debug mode.
22	ISRPEND	RO	0	Interrupt Pending
				Value Description
				0 No interrupt is pending.
				1 An interrupt is pending.
				This bit provides status for all interrupts excluding NMI and Faults.
21:18	reserved	RO	0x0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.

Bit/Field	Name	Туре	Reset	Description
17:12	VECPEND	RO	0x00	Interrupt Pending Vector Number  This field contains the exception number of the highest priority pending enabled exception. The value indicated by this field includes the effect of the BASEPRI and FAULTMASK registers, but not any effect of the PRIMASK register.
				Value Description
				0x00 No exceptions are pending
				0x01 Reserved
				0x02 NMI
				0x03 Hard fault
				0x04 Memory management fault
				0x05 Bus fault
				0x06 Usage fault
				0x07-0x0A Reserved
				0x0B SVCall
				0x0C Reserved for Debug
				0x0D Reserved
				0x0E PendSV
				0x0F SysTick
				0x10 Interrupt Vector 0
				0x11 Interrupt Vector 1
				•
				0x3B Interrupt Vector 43
				0x3C-0x3F Reserved
				0x30-0x3i ixeserved
11	RETBASE	RO	0	Return to Base
				Value Description
				O There are preempted active exceptions to execute.
				1 There are no active exceptions, or the currently executing exception is the only active exception.
				This bit provides status for all interrupts excluding NMI and Faults. This bit only has meaning if the processor is currently executing an ISR (the Interrupt Program Status (IPSR) register is non-zero).
10:6	reserved	RO	0x0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
5:0	VECACT	RO	0x00	Interrupt Pending Vector Number
				This field contains the active exception number. The exception numbers can be found in the description for the VECPEND field. If this field is clear, the processor is in Thread mode. This field contains the same value as the ISRNUM field in the <b>IPSR</b> register.
				Subtract 16 from this value to obtain the IRQ number required to index into the Interrupt Set Enable (ENn), Interrupt Clear Enable (DISn), Interrupt Set Pending (PENDn), Interrupt Clear Pending (UNPENDn), and Interrupt Priority (PRIn) registers (see page 55).


# Register 28: Vector Table Offset (VTABLE), offset 0xD08

**Note:** This register can only be accessed from privileged mode.

The **VTABLE** register indicates the offset of the vector table base address from memory address 0x0000.0000.

Vector Table Offset (VTABLE)

Base 0xE000.E000 Offset 0xD08 Type R/W, reset 0x0000.0000



Bit/Field	Name	Туре	Reset	Description
31:30	reserved	RO	0x0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
29	BASE	R/W	0	Vector Table Base
				<ul> <li>Value Description</li> <li>The vector table is in the code memory region.</li> <li>The vector table is in the SRAM memory region.</li> </ul>
28:8	OFFSET	R/W	0x000.00	Vector Table Offset  When configuring the OFFSET field, the offset must be aligned to the number of exception entries in the vector table. Because there are 43 interrupts, the offset must be aligned on a 256-byte boundary.
7:0	reserved	RO	0x00	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.

### Register 29: Application Interrupt and Reset Control (APINT), offset 0xD0C

Note: This register can only be accessed from privileged mode.

The **APINT** register provides priority grouping control for the exception model, endian status for data accesses, and reset control of the system. To write to this register, 0x05FA must be written to the VECTKEY field, otherwise the write is ignored.

The PRIGROUP field indicates the position of the binary point that splits the INTx fields in the Interrupt Priority (PRIx) registers into separate group priority and subpriority fields. Table 3-8 on page 119 shows how the PRIGROUP value controls this split. The bit numbers in the Group Priority Field and Subpriority Field columns in the table refer to the bits in the INTA field. For the INTB field, the corresponding bits are 15:13; for INTC, 23:21; and for INTD, 31:29.

**Note:** Determining preemption of an exception uses only the group priority field.

**Table 3-8. Interrupt Priority Levels** 


PRIGROUP Bit Field	Binary Point <sup>a</sup>	Group Priority Field	•	Group Priorities	Subpriorities
0x0 - 0x4	bxxx.	[7:5]	None	8	1
0x5	bxx.y	[7:6]	[5]	4	2
0x6	bx.yy	[7]	[6:5]	2	4
0x7	b.yyy	None	[7:5]	1	8

a. INTx field showing the binary point. An x denotes a group priority field bit, and a y denotes a subpriority field bit.

#### Application Interrupt and Reset Control (APINT)

Base 0xE000.E000 Offset 0xD0C

Type R/W, reset 0xFA05.0000



Bit/Field	Name	Type	Reset	Description
31:16	VECTKEY	R/W	0xFA05	Register Key
				This field is used to guard against accidental writes to this register. 0x05FA must be written to this field in order to change the bits in this register. On a read, 0xFA05 is returned.
15	ENDIANESS	RO	0	Data Endianess
				The Stellaris implementation uses only little-endian mode so this is cleared to $\boldsymbol{0}.$
14:11	reserved	RO	0x0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.

Bit/Field	Name	Туре	Reset	Description
10:8	PRIGROUP	R/W	0x0	Interrupt Priority Grouping  This field determines the split of group priority from subpriority (see Table 3-8 on page 119 for more information).
7:3	reserved	RO	0x0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
2	SYSRESREQ	WO	0	System Reset Request
				Value Description
				0 No effect.
				1 Resets the core and all on-chip peripherals except the Debug interface.
				This bit is automatically cleared during the reset of the core and reads as 0.
1	VECTCLRACT	WO	0	Clear Active NMI / Fault
				This bit is reserved for Debug use and reads as 0. This bit must be written as a 0, otherwise behavior is unpredictable.
0	VECTRESET	WO	0	System Reset  This bit is reserved for Debug use and reads as 0. This bit must be written as a 0, otherwise behavior is unpredictable.

## Register 30: System Control (SYSCTRL), offset 0xD10

**Note:** This register can only be accessed from privileged mode.

The SYSCTRL register controls features of entry to and exit from low-power state.

#### System Control (SYSCTRL)

Base 0xE000.E000

2

**SLEEPDEEP** 

R/W

Offset 0xD10 Type R/W, reset 0x0000.0000

	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16
		1						rese	rved						'	
Type	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO
Reset	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0
	15	14	13	12	11	10	9	8	7	6	5	4	3	2	1	0
		1	1		1	reserved		1	1	1		SEVONPEND	reserved	SLEEPDEEP	SLEEPEXIT	reserved
Type	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	R/W	RO	R/W	R/W	RO
Reset	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0

Bit/Field	Name	Type	Reset	Description
31:5	reserved	RO	0x0000.00	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
4	SEVONPEND	R/W	0	Wake Up on Pending
				Value Description
				Only enabled interrupts or events can wake up the processor:

Only enabled interrupts or events can wake up the processor; disabled interrupts are excluded.

1 Enabled events and all interrupts, including disabled interrupts, can wake up the processor.

When an event or interrupt enters the pending state, the event signal wakes up the processor from WFE. If the processor is not waiting for an event, the event is registered and affects the next WFE.

The processor also wakes up on execution of a SEV instruction or an external event.

3 RO 0 Software should not rely on the value of a reserved bit. To provide reserved compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.

Value Description

Deep Sleep Enable

Use Sleep mode as the low power mode.

Use Deep-sleep mode as the low power mode.

Bit/Field	Name	Туре	Reset	Description
1	SLEEPEXIT	R/W	0	Sleep on ISR Exit
				Value Description
				When returning from Handler mode to Thread mode, do not sleep when returning to Thread mode.
				When returning from Handler mode to Thread mode, enter sleep or deep sleep on return from an ISR.
				Setting this bit enables an interrupt-driven application to avoid returning to an empty main application.
0	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.

# Register 31: Configuration and Control (CFGCTRL), offset 0xD14


Note: This register can only be accessed from privileged mode.

The **CFGCTRL** register controls entry to Thread mode and enables: the handlers for NMI, hard fault and faults escalated by the **FAULTMASK** register to ignore bus faults; trapping of divide by zero and unaligned accesses; and access to the **SWTRIG** register by unprivileged software (see page 113).

#### Configuration and Control (CFGCTRL)

Base 0xE000.E000 Offset 0xD14

Type R/W, reset 0x0000.0000



Bit/Field	Name	Type	Reset	Description
31:10	reserved	RO	0x0000.00	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
9	STKALIGN	R/W	0	Stack Alignment on Exception Entry
				Value Description
				0 The stack is 4-byte aligned.
				1 The stack is 8-byte aligned.
				On exception entry, the processor uses bit 9 of the stacked <b>PSR</b> to indicate the stack alignment. On return from the exception, it uses this stacked bit to restore the correct stack alignment.
8	BFHFNMIGN	R/W	0	Ignore Bus Fault in NMI and Fault
				This bit enables handlers with priority -1 or -2 to ignore data bus faults caused by load and store instructions. The setting of this bit applies to the hard fault, NMI, and <b>FAULTMASK</b> escalated handlers.
				Value Description
				0 Data bus faults caused by load and store instructions cause a lock-up.
				1 Handlers running at priority -1 and -2 ignore data bus faults caused by load and store instructions.
				Set this bit only when the handler and its data are in absolutely safe memory. The normal use of this bit is to probe system devices and bridges to detect control path problems and fix them.
7:5	reserved	RO	0x0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should b preserved across a read-modify-write operation.

Bit/Field	Name	Туре	Reset	Description
4	DIV0	R/W	0	Trap on Divide by 0  This bit enables faulting or halting when the processor executes an SDIV or UDIV instruction with a divisor of 0.
				Value Description  O Do not trap on divide by 0. A divide by zero returns a quotient
				of 0.
				1 Trap on divide by 0.
3	UNALIGNED	R/W	0	Trap on Unaligned Access
				Value Description
				0 Do not trap on unaligned halfword and word accesses.
				1 Trap on unaligned halfword and word accesses. An unaligned access generates a usage fault.
				Unaligned LDM, STM, LDRD, and STRD instructions always fault regardless of whether <code>UNALIGNED</code> is set.
2	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
1	MAINPEND	R/W	0	Allow Main Interrupt Trigger
				Value Description
				0 Disables unprivileged software access to the <b>SWTRIG</b> register.
				1 Enables unprivileged software access to the <b>SWTRIG</b> register (see page 113).
0	BASETHR	R/W	0	Thread State Control
				Value Description
				The processor can enter Thread mode only when no exception is active.
				The processor can enter Thread mode from any level under the control of an EXC_RETURN value (see "Exception Return" on page 79 for more information).

## Register 32: System Handler Priority 1 (SYSPRI1), offset 0xD18

Note: This register can only be accessed from privileged mode.

The SYSPRI1 register configures the priority level, 0 to 7 of the usage fault, bus fault, and memory management fault exception handlers. This register is byte-accessible.

System Handler Priority 1 (SYSPRI1)

Base 0xE000.E000 Offset 0xD18

Туре	R/W, rese	et 0x0000	0.0000													
	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16
			1	rese	rved		1 1			USAGE	l			reserved		1
Туре	RO	RO	RO	RO	RO	RO	RO	RO	R/W	R/W	R/W	RO	RO	RO	RO	RO
Reset	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0
1	15	14	13 T	12	11	10	9	8	7 	6 I	5	4	3	2	1	0
		BUS				reserved				MEM				reserved		
Type Reset	R/W 0	R/W 0	R/W 0	RO 0	RO 0	RO 0	RO 0	RO 0	R/W 0	R/W 0	R/W 0	RO 0	RO 0	RO 0	RO 0	RO 0
_					_			_								
E	Bit/Field		Nam	ne	Ty	pe	Reset	Des	cription							
	31:24		reserv	ved	R	0	0x00	com	patibility	with futu	ure prod	he value ucts, the dify-write	value of	a reserv		
	23:21		USA	GE	R/	W	0x0	Usa	ge Fault	Priority						
									rity value	•		rity level o je 0-7, wi		•	_	
	20:16		reserv	ved	R	0	0x0	com	patibility	with futu	ure prod	he value ucts, the dify-write	value of	a reserv		
	15:13		BU	S	R/	W	0x0	Bus	Fault P	riority						
								This	field co	nfigures t	•	y level of with lowe			_	
	12:8		reserv	ved	R	0	0x0	com	patibility	with futu	ure prod	he value ucts, the dify-write	value of	a reserv		
	7:5		MEI	М	R/	W	0x0	Mer	nory Ma	nagemer	nt Fault I	Priority				
								Con	ıfigurabl	-	values a	ity level o		-	-	
	4:0		reserv	ved	R	0	0x0		patibility	with fut	ure prod	he value	value of	a reserv	•	

preserved across a read-modify-write operation.


# Register 33: System Handler Priority 2 (SYSPRI2), offset 0xD1C

**Note:** This register can only be accessed from privileged mode.

The SYSPRI2 register configures the priority level, 0 to 7 of the SVCall handler. This register is byte-accessible.

### System Handler Priority 2 (SYSPRI2)

Base 0xE000.E000 Offset 0xD1C Type R/W, reset 0x0000.0000



Bit/Field	Name	Type	Reset	Description
31:29	SVC	R/W	0x0	SVCall Priority
				This field configures the priority level of SVCall. Configurable priority values are in the range 0-7, with lower values having higher priority.
28:0	reserved	RO	0x000.0000	Software should not rely on the value of a reserved bit. To provide

compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.

# Register 34: System Handler Priority 3 (SYSPRI3), offset 0xD20

**Note:** This register can only be accessed from privileged mode.

The SYSPRI3 register configures the priority level, 0 to 7 of the SysTick exception and PendSV handlers. This register is byte-accessible.

### System Handler Priority 3 (SYSPRI3)

Base 0xE000.E000 Offset 0xD20

	R/W, res	et 0x0000	.0000													
	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16
		TICK				reserve	ed			PENDSV	1			reserved		•
Туре	R/W	R/W	R/W	RO	RO	RO	RO	RO	R/W	R/W	R/W	RO	RO	RO	RO	RO
Reset	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0
	15	14	13	12	11	10	9	8	7	6	5	4	3	2	1	0
	reserved									DEBUG	•		' '	reserved		1
Type Reset	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	R/W 0	R/W 0	R/W 0	RO 0	RO 0	RO 0	RO 0	RO 0
E	Bit/Field		Nam	ne	Ту	ре	Reset	Des	scription							
	31:29		TIC	K	R/	W	0x0	Sys	Tick Exc	eption P	riority					
								Cor	nfigurable	•	values a	•	,	sTick ex -7, with lo	•	
	28:24		reserv	ved	R	0	0x0	con	npatibility		ure prod	ucts, the	value of			vide hould be
	23:21		PEND	SV	R/	W	0x0	Per	ndSV Pri	ority						
										•		•		SV. Confi having h	_	
	20:8		reserv	ved	R	0	0x000	con	npatibility		ure prod	ucts, the	value of			vide hould be
	7:5		DEBU	JG	R/	W	0x0	Deb	oug Prior	ity						
										•	•	•		g. Configi having h		
	4:0		reserv	ved	R	0	0x0.0000							erved bit. a reserv		vide hould be

preserved across a read-modify-write operation.

## Register 35: System Handler Control and State (SYSHNDCTRL), offset 0xD24

**Note:** This register can only be accessed from privileged mode.

The **SYSHNDCTRL** register enables the system handlers, and indicates the pending status of the usage fault, bus fault, memory management fault, and SVC exceptions as well as the active status of the system handlers.

If a system handler is disabled and the corresponding fault occurs, the processor treats the fault as a hard fault.

This register can be modified to change the pending or active status of system exceptions. An OS kernel can write to the active bits to perform a context switch that changes the current exception type.

Caution – Software that changes the value of an active bit in this register without correct adjustment to the stacked content can cause the processor to generate a fault exception. Ensure software that writes to this register retains and subsequently restores the current active status.


If the value of a bit in this register must be modified after enabling the system handlers, a read-modify-write procedure must be used to ensure that only the required bit is modified.

#### System Handler Control and State (SYSHNDCTRL)

Base 0xE000.E000

Offset 0xD24

Type R/W, reset 0x0000.0000



Bit/Field	Name	Туре	Reset	Description
31:19	reserved	RO	0x000	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
18	USAGE	R/W	0	Usage Fault Enable
				Value Description
				0 Disables the usage fault exception.
				1 Enables the usage fault exception.
17	BUS	R/W	0	Bus Fault Enable
				Value Description
				0 Disables the bus fault exception.

Enables the bus fault exception.

Bit/Field	Name	Туре	Reset	Description
16	MEM	R/W	0	Memory Management Fault Enable
				Value Description
				0 Disables the memory management fault exception.
				1 Enables the memory management fault exception.
15	SVC	R/W	0	SVC Call Pending
				Value Description
				0 An SVC call exception is not pending.
				1 An SVC call exception is pending.
				This bit can be modified to change the pending status of the SVC call exception.
14	BUSP	R/W	0	Bus Fault Pending
				Value Description
				0 A bus fault exception is not pending.
				1 A bus fault exception is pending.
				This bit can be modified to change the pending status of the bus fault exception.
13	MEMP	R/W	0	Memory Management Fault Pending
				Value Description
				O A memory management fault exception is not pending.
				1 A memory management fault exception is pending.
				This bit can be modified to change the pending status of the memory management fault exception.
12	USAGEP	R/W	0	Usage Fault Pending
				Value Description
				0 A usage fault exception is not pending.
				1 A usage fault exception is pending.
				This bit can be modified to change the pending status of the usage fault exception.
11	TICK	R/W	0	SysTick Exception Active
				Value Description
				0 A SysTick exception is not active.
				1 A SysTick exception is active.
				This bit can be modified to change the active status of the SysTick exception, however, see the Caution above before setting this bit.

November 18, 2011 129

Bit/Field	Name	Туре	Reset	Description
10	PNDSV	R/W	0	PendSV Exception Active
				Value Description
				0 A PendSV exception is not active.
				1 A PendSV exception is active.
				This bit can be modified to change the active status of the PendSV exception, however, see the Caution above before setting this bit.
9	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
8	MON	R/W	0	Debug Monitor Active
				Value Description
				0 The Debug monitor is not active.
				1 The Debug monitor is active.
7	SVCA	R/W	0	SVC Call Active
				Value Description
				0 SVC call is not active.
				1 SVC call is active.
				This bit can be modified to change the active status of the SVC call exception, however, see the Caution above before setting this bit.
6:4	reserved	RO	0x0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
3	USGA	R/W	0	Usage Fault Active
				Value Description
				0 Usage fault is not active.
				1 Usage fault is active.
				This bit can be modified to change the active status of the usage fault exception, however, see the Caution above before setting this bit.
2	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
1	BUSA	R/W	0	Bus Fault Active
				Value Description
				0 Bus fault is not active.
				1 Bus fault is active.
				This bit can be modified to change the active status of the bus fault exception, however, see the Caution above before setting this bit.

Bit/Field	Name	Туре	Reset	Description
0	MEMA	R/W	0	Memory Management Fault Active
				Value Description  0 Memory management fault is not active.  1 Memory management fault is active.  This bit can be modified to change the active status of the memory management fault exception, however, see the Caution above before setting this bit.

November 18, 2011 131

### Register 36: Configurable Fault Status (FAULTSTAT), offset 0xD28

**Note:** This register can only be accessed from privileged mode.

The **FAULTSTAT** register indicates the cause of a memory management fault, bus fault, or usage fault. Each of these functions is assigned to a subregister as follows:

- Usage Fault Status (UFAULTSTAT), bits 31:16
- Bus Fault Status (BFAULTSTAT), bits 15:8
- Memory Management Fault Status (MFAULTSTAT), bits 7:0

**FAULTSTAT** is byte accessible. **FAULTSTAT** or its subregisters can be accessed as follows:

- The complete **FAULTSTAT** register, with a word access to offset 0xD28
- The **MFAULTSTAT**, with a byte access to offset 0xD28
- The MFAULTSTAT and BFAULTSTAT, with a halfword access to offset 0xD28
- The **BFAULTSTAT**, with a byte access to offset 0xD29
- The **UFAULTSTAT**, with a halfword access to offset 0xD2A

Bits are cleared by writing a 1 to them.

In a fault handler, the true faulting address can be determined by:


- Read and save the Memory Management Fault Address (MMADDR) or Bus Fault Address (FAULTADDR) value.
- 2. Read the MMARV bit in MFAULTSTAT, or the BFARV bit in BFAULTSTAT to determine if the MMADDR or FAULTADDR contents are valid.

Software must follow this sequence because another higher priority exception might change the **MMADDR** or **FAULTADDR** value. For example, if a higher priority handler preempts the current fault handler, the other fault might change the **MMADDR** or **FAULTADDR** value.

#### Configurable Fault Status (FAULTSTAT)

Base 0xE000.E000 Offset 0xD28

Type R/W1C, reset 0x0000.0000



Bit/Field	Name	Туре	Reset	Description
25	DIV0	R/W1C	0	Divide-by-Zero Usage Fault
				Value Description
				No divide-by-zero fault has occurred, or divide-by-zero trapping is not enabled.
				1 The processor has executed an SDIV or UDIV instruction with a divisor of 0.
				When this bit is set, the <b>PC</b> value stacked for the exception return points to the instruction that performed the divide by zero.
				Trapping on divide-by-zero is enabled by setting the DIV0 bit in the Configuration and Control (CFGCTRL) register (see page 123).
				This bit is cleared by writing a 1 to it.
24	UNALIGN	R/W1C	0	Unaligned Access Usage Fault
				Value Description
				No unaligned access fault has occurred, or unaligned access trapping is not enabled.
				1 The processor has made an unaligned memory access.
				Unaligned LDM, STM, LDRD, and STRD instructions always fault regardless of the configuration of this bit.
				Trapping on unaligned access is enabled by setting the UNALIGNED bit in the CFGCTRL register (see page 123).
				This bit is cleared by writing a 1 to it.
23:20	reserved	RO	0x00	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
19	NOCP	R/W1C	0	No Coprocessor Usage Fault
				Value Description
				O A usage fault has not been caused by attempting to access a coprocessor.
				1 The processor has attempted to access a coprocessor.
				This bit is cleared by writing a 1 to it.
18	INVPC	R/W1C	0	Invalid PC Load Usage Fault
				Value Description
				O A usage fault has not been caused by attempting to load an invalid PC value.
				The processor has attempted an illegal load of EXC_RETURN to the PC as a result of an invalid context or an invalid EXC_RETURN value.
				When this bit is set, the <b>PC</b> value stacked for the exception return points to the instruction that tried to perform the illegal load of the <b>PC</b> .
				This bit is cleared by writing a 1 to it.

November 18, 2011 133

Bit/Field	Name	Туре	Reset	Description
17	INVSTAT	R/W1C	0	Invalid State Usage Fault
				Value Description
				O A usage fault has not been caused by an invalid state.
				1 The processor has attempted to execute an instruction that makes illegal use of the EPSR register.
				When this bit is set, the <b>PC</b> value stacked for the exception return points to the instruction that attempted the illegal use of the <b>Execution Program Status Register (EPSR)</b> register.
				This bit is not set if an undefined instruction uses the <b>EPSR</b> register.
				This bit is cleared by writing a 1 to it.
16	UNDEF	R/W1C	0	Undefined Instruction Usage Fault
				Value Description
				0 A usage fault has not been caused by an undefined instruction.
				1 The processor has attempted to execute an undefined instruction.
				When this bit is set, the <b>PC</b> value stacked for the exception return points to the undefined instruction.
				An undefined instruction is an instruction that the processor cannot decode.
				This bit is cleared by writing a 1 to it.
15	BFARV	R/W1C	0	Bus Fault Address Register Valid
				Value Description
				The value in the Bus Fault Address (FAULTADDR) register is not a valid fault address.
				1 The <b>FAULTADDR</b> register is holding a valid fault address.
				This bit is set after a bus fault, where the address is known. Other faults can clear this bit, such as a memory management fault occurring later.
				If a bus fault occurs and is escalated to a hard fault because of priority, the hard fault handler must clear this bit. This action prevents problems if returning to a stacked active bus fault handler whose <b>FAULTADDR</b> register value has been overwritten.
				This bit is cleared by writing a 1 to it.
14:13	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.

Bit/Field	Name	Type	Reset	Description
12	BSTKE	R/W1C	0	Stack Bus Fault
				<ul> <li>Value Description</li> <li>No bus fault has occurred on stacking for exception entry.</li> <li>Stacking for an exception entry has caused one or more bus</li> </ul>
				faults.
				When this bit is set, the <b>SP</b> is still adjusted but the values in the context area on the stack might be incorrect. A fault address is not written to the <b>FAULTADDR</b> register.
				This bit is cleared by writing a 1 to it.
11	BUSTKE	R/W1C	0	Unstack Bus Fault
				Value Description
				No bus fault has occurred on unstacking for a return from exception.
				1 Unstacking for a return from exception has caused one or more bus faults.
				This fault is chained to the handler. Thus, when this bit is set, the original return stack is still present. The <b>SP</b> is not adjusted from the failing return, a new save is not performed, and a fault address is not written to the <b>FAULTADDR</b> register.
				This bit is cleared by writing a 1 to it.
10	IMPRE	R/W1C	0	Imprecise Data Bus Error
				Value Description
				O An imprecise data bus error has not occurred.
				A data bus error has occurred, but the return address in the stack frame is not related to the instruction that caused the error.
				When this bit is set, a fault address is not written to the <b>FAULTADDR</b> register.
				This fault is asynchronous. Therefore, if the fault is detected when the priority of the current process is higher than the bus fault priority, the bus fault becomes pending and becomes active only when the processor returns from all higher-priority processes. If a precise fault occurs before the processor enters the handler for the imprecise bus fault, the handler detects that both the IMPRE bit is set and one of the precise fault status bits is set.
				This bit is cleared by writing a 1 to it.
9	PRECISE	R/W1C	0	Precise Data Bus Error
				Value Description
				O A precise data bus error has not occurred.
				A data bus error has occurred, and the PC value stacked for the exception return points to the instruction that caused the fault.
				When this bit is set, the fault address is written to the <b>FAULTADDR</b> register.
				This hit is alcored by writing a 1 to it

November 18, 2011 135

This bit is cleared by writing a 1 to it.

Bit/Field	Name	Туре	Reset	Description
8	IBUS	R/W1C	0	Instruction Bus Error
				Value Description
				O An instruction bus error has not occurred.
				1 An instruction bus error has occurred.
				The processor detects the instruction bus error on prefetching an instruction, but sets this bit only if it attempts to issue the faulting instruction.
				When this bit is set, a fault address is not written to the <b>FAULTADDR</b> register.
				This bit is cleared by writing a 1 to it.
7	MMARV	R/W1C	0	Memory Management Fault Address Register Valid
				Value Description
				0 The value in the Memory Management Fault Address (MMADDR) register is not a valid fault address.
				1 The <b>MMADDR</b> register is holding a valid fault address.
				If a memory management fault occurs and is escalated to a hard fault because of priority, the hard fault handler must clear this bit. This action prevents problems if returning to a stacked active memory management fault handler whose <b>MMADDR</b> register value has been overwritten.
				This bit is cleared by writing a 1 to it.
6:5	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
4	MSTKE	R/W1C	0	Stack Access Violation
				Value Description
				No memory management fault has occurred on stacking for exception entry.
				Stacking for an exception entry has caused one or more access violations.
				When this bit is set, the <b>SP</b> is still adjusted but the values in the context area on the stack might be incorrect. A fault address is not written to the <b>MMADDR</b> register.

This bit is cleared by writing a 1 to it.

Bit/Field	Name	Туре	Reset	Description
3	MUSTKE	R/W1C	0	Unstack Access Violation
				Value Description
				No memory management fault has occurred on unstacking for a return from exception.
				1 Unstacking for a return from exception has caused one or more access violations.
				This fault is chained to the handler. Thus, when this bit is set, the original return stack is still present. The <b>SP</b> is not adjusted from the failing return, a new save is not performed, and a fault address is not written to the <b>MMADDR</b> register.
				This bit is cleared by writing a 1 to it.
2	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
1	DERR	R/W1C	0	Data Access Violation
				Value Description
				0 A data access violation has not occurred.
				1 The processor attempted a load or store at a location that does not permit the operation.
				When this bit is set, the <b>PC</b> value stacked for the exception return points to the faulting instruction and the address of the attempted access is written to the <b>MMADDR</b> register.
				This bit is cleared by writing a 1 to it.
0	IERR	R/W1C	0	Instruction Access Violation
				Value Description
				O An instruction access violation has not occurred.
				1 The processor attempted an instruction fetch from a location that does not permit execution.
				This fault occurs on any access to an XN region, even when the MPU is disabled or not present.
				When this bit is set, the <b>PC</b> value stacked for the exception return points to the faulting instruction and the address of the attempted access is

This bit is cleared by writing a 1 to it.

not written to the **MMADDR** register.

# Register 37: Hard Fault Status (HFAULTSTAT), offset 0xD2C

**Note:** This register can only be accessed from privileged mode.

The **HFAULTSTAT** register gives information about events that activate the hard fault handler.

Bits are cleared by writing a 1 to them.

Hard Fault Status (HFAULTSTAT)

Base 0xE000.E000

Offset 0xD2C Type R/W1C, reset 0x0000.0000

,,	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16	
	DBG	FORCED					1 1		rese		î				î	ì	
Type Reset	R/W1C 0	R/W1C 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0							
. 10001	15	14	13	12	11	10	9	8	7	6	5	4	3	2	1	0	
		1 1	1				reser				1	1	-	_	VECT	reserved	
Type Reset	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	R/W1C 0	RO 0	
E	Bit/Field		Nam	ne	e Type		Reset	Des	Description								
	31		DBO	3	R/W	/10	0	Deh	ug Even	t							
	31		DDC	,	17/71	10	U		Ū		or Debud	g use. Th	is bit mu	ıst be wı	ritten as	a 0	
									rwise be		,	•				<b></b> 0,	
	30		FORC	ED	R/W	/1C	0	Ford	ed Hard	Fault							
								Valu	ue Desc	ription							
								0	No fo	rced ha	rd fault h	as occur	red.				
								1	A for	ced hard	l fault ha	s been g	enerate	d by esc	alation o	f a fault	
										_		ity that ca it is disa		handled	l, either b	ecause	
												fault han		st read t	he other	fault	
									bit is cle								
	29:2		reserv	erved		0	0x00	com	Software should not compatibility with future preserved across a re		ure prod	ucts, the	value of	a reserv			
	1		VEC	т	R/W	/1C	0	Vect	or Table	Read F	ault						
								Valu	ue Desc	ription							
								0	No b	us fault l	nas occu	irred on a	a vector	table rea	ad.		
								1	A bus	s fault o	ccurred o	on a vect	or table	read.			
								This	error is	always l	nandled	by the ha	ard fault	handler.			
												lue stack eempted				n points	
									bit is cle			•	<i>y</i>				
	0		reserv	/ed	R	0	0	com	patibility	with fut	ure prod	he value ucts, the dify-write	value of	a reserv			


## Register 38: Memory Management Fault Address (MMADDR), offset 0xD34

**Note:** This register can only be accessed from privileged mode.

The MMADDR register contains the address of the location that generated a memory management fault. When an unaligned access faults, the address in the MMADDR register is the actual address that faulted. Because a single read or write instruction can be split into multiple aligned accesses, the fault address can be any address in the range of the requested access size. Bits in the Memory Management Fault Status (MFAULTSTAT) register indicate the cause of the fault and whether the value in the MMADDR register is valid (see page 132).

Memory Management Fault Address (MMADDR)

Base 0xE000.E000 Offset 0xD34 Type R/W, reset -




When the  ${\tt MMARV}$  bit of **MFAULTSTAT** is set, this field holds the address of the location that generated the memory management fault.


### Register 39: Bus Fault Address (FAULTADDR), offset 0xD38

**Note:** This register can only be accessed from privileged mode.

The **FAULTADDR** register contains the address of the location that generated a bus fault. When an unaligned access faults, the address in the **FAULTADDR** register is the one requested by the instruction, even if it is not the address of the fault. Bits in the **Bus Fault Status (BFAULTSTAT)** register indicate the cause of the fault and whether the value in the **FAULTADDR** register is valid (see page 132).



Base 0xE000.E000 Offset 0xD38 Type R/W, reset -



When the FAULTADDRV bit of **BFAULTSTAT** is set, this field holds the address of the location that generated the bus fault.

# 3.6 Memory Protection Unit (MPU) Register Descriptions

This section lists and describes the Memory Protection Unit (MPU) registers, in numerical order by address offset.

The MPU registers can only be accessed from privileged mode.


# Register 40: MPU Type (MPUTYPE), offset 0xD90

**Note:** This register can only be accessed from privileged mode.

The **MPUTYPE** register indicates whether the MPU is present, and if so, how many regions it supports.

### MPU Type (MPUTYPE)

Base 0xE000.E000 Offset 0xD90 Type RO, reset 0x0000.0800



Bit/Field	Name	Type	Reset	Description
31:24	reserved	RO	0x00	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
23:16	IREGION	RO	0x00	Number of I Regions
				This field indicates the number of supported MPU instruction regions. This field always contains 0x00. The MPU memory map is unified and is described by the DREGION field.
15:8	DREGION	RO	0x08	Number of D Regions
				Value Description
				0x08 Indicates there are eight supported MPU data regions.
7:1	reserved	RO	0x00	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
0	SEPARATE	RO	0	Separate or Unified MPU

Value Description

0 Indicates the MPU is unified.

## Register 41: MPU Control (MPUCTRL), offset 0xD94

**Note:** This register can only be accessed from privileged mode.

The **MPUCTRL** register enables the MPU, enables the default memory map background region, and enables use of the MPU when in the hard fault, Non-maskable Interrupt (NMI), and **Fault Mask Register (FAULTMASK)** escalated handlers.

When the ENABLE and PRIVDEFEN bits are both set:

- For privileged accesses, the default memory map is as described in "Memory Model" on page 63. Any access by privileged software that does not address an enabled memory region behaves as defined by the default memory map.
- Any access by unprivileged software that does not address an enabled memory region causes a memory management fault.

Execute Never (XN) and Strongly Ordered rules always apply to the System Control Space regardless of the value of the ENABLE bit.

When the ENABLE bit is set, at least one region of the memory map must be enabled for the system to function unless the PRIVDEFEN bit is set. If the PRIVDEFEN bit is set and no regions are enabled, then only privileged software can operate.


When the ENABLE bit is clear, the system uses the default memory map, which has the same memory attributes as if the MPU is not implemented (see Table 2-5 on page 65 for more information). The default memory map applies to accesses from both privileged and unprivileged software.

When the MPU is enabled, accesses to the System Control Space and vector table are always permitted. Other areas are accessible based on regions and whether PRIVDEFEN is set.

Unless HFNMIENA is set, the MPU is not enabled when the processor is executing the handler for an exception with priority -1 or -2. These priorities are only possible when handling a hard fault or NMI exception or when **FAULTMASK** is enabled. Setting the HFNMIENA bit enables the MPU when operating with these two priorities.

#### MPU Control (MPUCTRL)

Base 0xE000.E000 Offset 0xD94



compatibility with future products, the value of a reserved bit should be

preserved across a read-modify-write operation.

Bit/Field	Name	Type	Reset	Description
2	PRIVDEFEN	R/W	0	MPU Default Region This bit enables privileged software access to the default memory map.
				Value Description
				0 If the MPU is enabled, this bit disables use of the default memory map. Any memory access to a location not covered by any enabled region causes a fault.
				1 If the MPU is enabled, this bit enables use of the default memory map as a background region for privileged software accesses.
				When this bit is set, the background region acts as if it is region number -1. Any region that is defined and enabled has priority over this default map.
				If the MPU is disabled, the processor ignores this bit.
1	HFNMIENA	R/W	0	MPU Enabled During Faults
				This bit controls the operation of the MPU during hard fault, NMI, and <b>FAULTMASK</b> handlers.
				Value Description
				The MPU is disabled during hard fault, NMI, and <b>FAULTMASK</b> handlers, regardless of the value of the ENABLE bit.
				1 The MPU is enabled during hard fault, NMI, and FAULTMASK handlers.
				When the MPU is disabled and this bit is set, the resulting behavior is unpredictable.
0	ENABLE	R/W	0	MPU Enable
				Value Description
				0 The MPU is disabled.
				1 The MPU is enabled.
				When the MPU is disabled and the HFNMIENA bit is set, the resulting behavior is unpredictable.

November 18, 2011 143

## Register 42: MPU Region Number (MPUNUMBER), offset 0xD98


**Note:** This register can only be accessed from privileged mode.

The MPUNUMBER register selects which memory region is referenced by the MPU Region Base Address (MPUBASE) and MPU Region Attribute and Size (MPUATTR) registers. Normally, the required region number should be written to this register before accessing the MPUBASE or the MPUATTR register. However, the region number can be changed by writing to the MPUBASE register with the VALID bit set (see page 145). This write updates the value of the REGION field.

#### MPU Region Number (MPUNUMBER)

Base 0xE000.E000 Offset 0xD98

Type R/W, reset 0x0000.0000



Bit/Field	Name	Type	Reset	Description
31:3	reserved	RO	0x0000.000	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
2:0	NUMBER	R/W	0x0	MPU Region to Access

This field indicates the MPU region referenced by the  $\bf MPUBASE$  and  $\bf MPUATTR$  registers. The MPU supports eight memory regions.

Register 43: MPU Region Base Address (MPUBASE), offset 0xD9C

Register 44: MPU Region Base Address Alias 1 (MPUBASE1), offset 0xDA4

Register 45: MPU Region Base Address Alias 2 (MPUBASE2), offset 0xDAC

Register 46: MPU Region Base Address Alias 3 (MPUBASE3), offset 0xDB4

**Note:** This register can only be accessed from privileged mode.

The MPUBASE register defines the base address of the MPU region selected by the MPU Region Number (MPUNUMBER) register and can update the value of the MPUNUMBER register. To change the current region number and update the MPUNUMBER register, write the MPUBASE register with the VALID bit set.

The ADDR field is bits 31:*N* of the **MPUBASE** register. Bits (*N*-1):5 are reserved. The region size, as specified by the SIZE field in the **MPU Region Attribute and Size (MPUATTR)** register, defines the value of *N* where:

 $N = Log_2(Region size in bytes)$ 

If the region size is configured to 4 GB in the **MPUATTR** register, there is no valid ADDR field. In this case, the region occupies the complete memory map, and the base address is 0x0000.0000.

The base address is aligned to the size of the region. For example, a 64-KB region must be aligned on a multiple of 64 KB, for example, at 0x0001.0000 or 0x0002.0000.

Base Address Mask

#### MPU Region Base Address (MPUBASE)

**ADDR** 


R/W

0x0000.000

Base 0xE000.E000 Offset 0xD9C

31:5

Type R/W, reset 0x0000.0000



Bits 31:*N* in this field contain the region base address. The value of *N* depends on the region size, as shown above. The remaining bits (*N*-1):5 are reserved.

Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.

Bit/Field	Name	Туре	Reset	Description
4	VALID	WO	0	Region Number Valid
				Value Description
				The MPUNUMBER register is not changed and the processor updates the base address for the region specified in the MPUNUMBER register and ignores the value of the REGION field.
				The <b>MPUNUMBER</b> register is updated with the value of the REGION field and the base address is updated for the region specified in the REGION field.
				This bit is always read as 0.
3	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
2:0	REGION	R/W	0x0	Region Number  On a write, contains the value to be written to the <b>MPUNUMBER</b> register.  On a read, returns the current region number in the <b>MPUNUMBER</b> register.

Register 47: MPU Region Attribute and Size (MPUATTR), offset 0xDA0

Register 48: MPU Region Attribute and Size Alias 1 (MPUATTR1), offset 0xDA8

Register 49: MPU Region Attribute and Size Alias 2 (MPUATTR2), offset 0xDB0

Register 50: MPU Region Attribute and Size Alias 3 (MPUATTR3), offset 0xDB8

**Note:** This register can only be accessed from privileged mode.

The **MPUATTR** register defines the region size and memory attributes of the MPU region specified by the **MPU Region Number (MPUNUMBER)** register and enables that region and any subregions.

The **MPUATTR** register is accessible using word or halfword accesses with the most-significant halfword holding the region attributes and the least-significant halfword holds the region size and the region and subregion enable bits.

The MPU access permission attribute bits, XN, AP, TEX, S, C, and B, control access to the corresponding memory region. If an access is made to an area of memory without the required permissions, then the MPU generates a permission fault.

The SIZE field defines the size of the MPU memory region specified by the **MPUNUMBER** register as follows:

(Region size in bytes) =  $2^{(SIZE+1)}$ 

The smallest permitted region size is 32 bytes, corresponding to a SIZE value of 4. Table 3-9 on page 147 gives example SIZE values with the corresponding region size and value of N in the MPU Region Base Address (MPUBASE) register.

Table 3-9. Example SIZE Field Values


SIZE Encoding	Region Size	Value of N <sup>a</sup>	Note
00100b (0x4)	32 B	5	Minimum permitted size
01001b (0x9)	1 KB	10	-
10011b (0x13)	1 MB	20	-
11101b (0x1D)	1 GB	30	-
11111b (0x1F)	4 GB	No valid ADDR field in <b>MPUBASE</b> ; the region occupies the complete memory map.	Maximum possible size

a. Refers to the N parameter in the MPUBASE register (see page 145).

## MPU Region Attribute and Size (MPUATTR)

Base 0xE000.E000 Offset 0xDA0

Type R/W, reset 0x0000.0000



Bit/Field	Name	Туре	Reset	Description
31:29	reserved	RO	0x00	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
28	XN	R/W	0	Instruction Access Disable
				Value Description
				0 Instruction fetches are enabled.
				1 Instruction fetches are disabled.
27	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
26:24	AP	R/W	0	Access Privilege
				For information on using this bit field, see Table 3-5 on page 93.
23:22	reserved	RO	0x0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
21:19	TEX	R/W	0x0	Type Extension Mask
				For information on using this bit field, see Table 3-3 on page 92.
18	S	R/W	0	Shareable For information on using this bit, see Table 3-3 on page 92.
17	С	R/W	0	Cacheable
1,	Ü	1777	Ü	For information on using this bit, see Table 3-3 on page 92.
16	В	R/W	0	Bufferable
				For information on using this bit, see Table 3-3 on page 92.
15:8	SRD	R/W	0x00	Subregion Disable Bits
				Value Description
				O The corresponding subregion is enabled.
				1 The corresponding subregion is disabled.
				Region sizes of 128 bytes and less do not support subregions. When writing the attributes for such a region, configure the SRD field as 0x00. See the section called "Subregions" on page 91 for more information.
7:6	reserved	RO	0x0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
5:1	SIZE	R/W	0x0	Region Size Mask
				The SIZE field defines the size of the MPU memory region specified by the <b>MPUNUMBER</b> register. Refer to Table 3-9 on page 147 for more information.

Bit/Field	Name	Туре	Reset	Description
0	ENABLE	R/W	0	Region Enable
				Value Description  The region is disabled.  The region is enabled.

# 4 JTAG Interface

The Joint Test Action Group (JTAG) port is an IEEE standard that defines a Test Access Port and Boundary Scan Architecture for digital integrated circuits and provides a standardized serial interface for controlling the associated test logic. The TAP, Instruction Register (IR), and Data Registers (DR) can be used to test the interconnections of assembled printed circuit boards and obtain manufacturing information on the components. The JTAG Port also provides a means of accessing and controlling design-for-test features such as I/O pin observation and control, scan testing, and debugging.

The JTAG port is comprised of five pins: TRST, TCK, TMS, TDI, and TDO. Data is transmitted serially into the controller on TDI and out of the controller on TDO. The interpretation of this data is dependent on the current state of the TAP controller. For detailed information on the operation of the JTAG port and TAP controller, please refer to the *IEEE Standard 1149.1-Test Access Port and Boundary-Scan Architecture*.

The Stellaris JTAG controller works with the ARM JTAG controller built into the Cortex-M3 core. This is implemented by multiplexing the TDO outputs from both JTAG controllers. ARM JTAG instructions select the ARM TDO output while Stellaris JTAG instructions select the Stellaris TDO outputs. The multiplexer is controlled by the Stellaris JTAG controller, which has comprehensive programming for the ARM, Stellaris, and unimplemented JTAG instructions.


The Stellaris JTAG module has the following features:

- IEEE 1149.1-1990 compatible Test Access Port (TAP) controller
- Four-bit Instruction Register (IR) chain for storing JTAG instructions
- IEEE standard instructions: BYPASS, IDCODE, SAMPLE/PRELOAD, EXTEST and INTEST
- ARM additional instructions: APACC, DPACC and ABORT
- Integrated ARM Serial Wire Debug (SWD)

See the ARM® Debug Interface V5 Architecture Specification for more information on the ARM JTAG controller.

## 4.1 Block Diagram

Figure 4-1. JTAG Module Block Diagram



# 4.2 Signal Description

Table 4-1 on page 151 and Table 4-2 on page 152 list the external signals of the JTAG/SWD controller and describe the function of each. The JTAG/SWD controller signals are alternate functions for some GPIO signals, however note that the reset state of the pins is for the JTAG/SWD function. The JTAG/SWD controller signals are under commit protection and require a special process to be configured as GPIOs, see "Commit Control" on page 258. The column in the table below titled "Pin Assignment" lists the GPIO pin placement for the JTAG/SWD controller signals. The AFSEL bit in the **GPIO Alternate Function Select (GPIOAFSEL)** register (page 272) is set to choose the JTAG/SWD function. For more information on configuring GPIOs, see "General-Purpose Input/Outputs (GPIOs)" on page 251.

Table 4-1. JTAG\_SWD\_SWO Signals (100LQFP)

Pin Name	Pin Number	Pin Type	Buffer Type <sup>a</sup>	Description
SWCLK	80	1	TTL	JTAG/SWD CLK.
SWDIO	79	I/O	TTL	JTAG TMS and SWDIO.
SWO	77	0	TTL	JTAG TDO and SWO.
TCK	80	1	TTL	JTAG/SWD CLK.
TDI	78	1	TTL	JTAG TDI.
TDO	77	0	TTL	JTAG TDO and SWO.
TMS	79	I/O	TTL	JTAG TMS and SWDIO.
TRST	89	1	TTL	JTAG TRST.

a. The TTL designation indicates the pin has TTL-compatible voltage levels.

Table 4-2. JTAG\_SWD\_SWO Signals (108BGA)

Pin Name	Pin Number	Pin Type	Buffer Type <sup>a</sup>	Description
SWCLK	A9	1	TTL	JTAG/SWD CLK.
SWDIO	В9	I/O	TTL	JTAG TMS and SWDIO.
SWO	A10	0	TTL	JTAG TDO and SWO.
TCK	A9	1	TTL	JTAG/SWD CLK.
TDI	В8	I	TTL	JTAG TDI.
TDO	A10	0	TTL	JTAG TDO and SWO.
TMS	В9	I/O	TTL	JTAG TMS and SWDIO.
TRST	A8	1	TTL	JTAG TRST.

a. The TTL designation indicates the pin has TTL-compatible voltage levels.

# 4.3 Functional Description

A high-level conceptual drawing of the JTAG module is shown in Figure 4-1 on page 151. The JTAG module is composed of the Test Access Port (TAP) controller and serial shift chains with parallel update registers. The TAP controller is a simple state machine controlled by the TRST, TCK and TMS inputs. The current state of the TAP controller depends on the current value of TRST and the sequence of values captured on TMS at the rising edge of TCK. The TAP controller determines when the serial shift chains capture new data, shift data from TDI towards TDO, and update the parallel load registers. The current state of the TAP controller also determines whether the Instruction Register (IR) chain or one of the Data Register (DR) chains is being accessed.

The serial shift chains with parallel load registers are comprised of a single Instruction Register (IR) chain and multiple Data Register (DR) chains. The current instruction loaded in the parallel load register determines which DR chain is captured, shifted, or updated during the sequencing of the TAP controller.

Some instructions, like EXTEST and INTEST, operate on data currently in a DR chain and do not capture, shift, or update any of the chains. Instructions that are not implemented decode to the BYPASS instruction to ensure that the serial path between TDI and TDO is always connected (see Table 4-4 on page 158 for a list of implemented instructions).

See "JTAG and Boundary Scan" on page 565 for JTAG timing diagrams.

#### 4.3.1 JTAG Interface Pins

The JTAG interface consists of five standard pins: TRST,TCK, TMS, TDI, and TDO. These pins and their associated reset state are given in Table 4-3 on page 152. Detailed information on each pin follows.

Table 4-3. JTAG Port Pins Reset State

Pin Name	Data Direction	Internal Pull-Up	Internal Pull-Down	Drive Strength	Drive Value
TRST	Input	Enabled	Disabled	N/A	N/A
TCK	Input	Enabled	Disabled	N/A	N/A
TMS	Input	Enabled	Disabled	N/A	N/A
TDI	Input	Enabled	Disabled	N/A	N/A
TDO	Output	Enabled	Disabled	2-mA driver	High-Z

## 4.3.1.1 Test Reset Input (TRST)

The  $\overline{\mathtt{TRST}}$  pin is an asynchronous active Low input signal for initializing and resetting the JTAG TAP controller and associated JTAG circuitry. When  $\overline{\mathtt{TRST}}$  is asserted, the TAP controller resets to the Test-Logic-Reset state and remains there while  $\overline{\mathtt{TRST}}$  is asserted. When the TAP controller enters the Test-Logic-Reset state, the JTAG Instruction Register (IR) resets to the default instruction, IDCODE.

By default, the internal pull-up resistor on the TRST pin is enabled after reset. Changes to the pull-up resistor settings on GPIO Port B should ensure that the internal pull-up resistor remains enabled on PB7/TRST; otherwise JTAG communication could be lost.

## 4.3.1.2 Test Clock Input (TCK)

The TCK pin is the clock for the JTAG module. This clock is provided so the test logic can operate independently of any other system clocks. In addition, it ensures that multiple JTAG TAP controllers that are daisy-chained together can synchronously communicate serial test data between components. During normal operation, TCK is driven by a free-running clock with a nominal 50% duty cycle. When necessary, TCK can be stopped at 0 or 1 for extended periods of time. While TCK is stopped at 0 or 1, the state of the TAP controller does not change and data in the JTAG Instruction and Data Registers is not lost.

By default, the internal pull-up resistor on the  ${ t TCK}$  pin is enabled after reset. This assures that no clocking occurs if the pin is not driven from an external source. The internal pull-up and pull-down resistors can be turned off to save internal power as long as the  ${ t TCK}$  pin is constantly being driven by an external source.

#### 4.3.1.3 Test Mode Select (TMS)

The TMS pin selects the next state of the JTAG TAP controller. TMS is sampled on the rising edge of TCK. Depending on the current TAP state and the sampled value of TMS, the next state is entered. Because the TMS pin is sampled on the rising edge of TCK, the *IEEE Standard 1149.1* expects the value on TMS to change on the falling edge of TCK.

Holding TMS high for five consecutive TCK cycles drives the TAP controller state machine to the Test-Logic-Reset state. When the TAP controller enters the Test-Logic-Reset state, the JTAG Instruction Register (IR) resets to the default instruction, IDCODE. Therefore, this sequence can be used as a reset mechanism, similar to asserting TRST. The JTAG Test Access Port state machine can be seen in its entirety in Figure 4-2 on page 155.

By default, the internal pull-up resistor on the TMS pin is enabled after reset. Changes to the pull-up resistor settings on GPIO Port C should ensure that the internal pull-up resistor remains enabled on PC1/TMS; otherwise JTAG communication could be lost.

## 4.3.1.4 Test Data Input (TDI)

The TDI pin provides a stream of serial information to the IR chain and the DR chains. TDI is sampled on the rising edge of TCK and, depending on the current TAP state and the current instruction, presents this data to the proper shift register chain. Because the TDI pin is sampled on the rising edge of TCK, the *IEEE Standard 1149.1* expects the value on TDI to change on the falling edge of TCK.

By default, the internal pull-up resistor on the TDI pin is enabled after reset. Changes to the pull-up resistor settings on GPIO Port C should ensure that the internal pull-up resistor remains enabled on PC2/TDI; otherwise JTAG communication could be lost.

## 4.3.1.5 Test Data Output (TDO)

The TDO pin provides an output stream of serial information from the IR chain or the DR chains. The value of TDO depends on the current TAP state, the current instruction, and the data in the chain being accessed. In order to save power when the JTAG port is not being used, the TDO pin is placed in an inactive drive state when not actively shifting out data. Because TDO can be connected to the TDI of another controller in a daisy-chain configuration, the *IEEE Standard 1149.1* expects the value on TDO to change on the falling edge of TCK.

By default, the internal pull-up resistor on the <code>TDO</code> pin is enabled after reset. This assures that the pin remains at a constant logic level when the JTAG port is not being used. The internal pull-up and pull-down resistors can be turned off to save internal power if a High-Z output value is acceptable during certain TAP controller states.

#### 4.3.2 JTAG TAP Controller

The JTAG TAP controller state machine is shown in Figure 4-2 on page 155. The TAP controller state machine is reset to the Test-Logic-Reset state on the assertion of a Power-On-Reset (POR) or the assertion of TRST. Asserting the correct sequence on the TMS pin allows the JTAG module to shift in new instructions, shift in data, or idle during extended testing sequences. For detailed information on the function of the TAP controller and the operations that occur in each state, please refer to *IEEE Standard 1149.1*.




Figure 4-2. Test Access Port State Machine

## 4.3.3 Shift Registers

The Shift Registers consist of a serial shift register chain and a parallel load register. The serial shift register chain samples specific information during the TAP controller's CAPTURE states and allows this information to be shifted out of TDO during the TAP controller's SHIFT states. While the sampled data is being shifted out of the chain on TDO, new data is being shifted into the serial shift register on TDI. This new data is stored in the parallel load register during the TAP controller's UPDATE states. Each of the shift registers is discussed in detail in "Register Descriptions" on page 158.

## 4.3.4 Operational Considerations

There are certain operational considerations when using the JTAG module. Because the JTAG pins can be programmed to be GPIOs, board configuration and reset conditions on these pins must be considered. In addition, because the JTAG module has integrated ARM Serial Wire Debug, the method for switching between these two operational modes is described below.

### 4.3.4.1 **GPIO** Functionality

When the controller is reset with either a POR or  $\overline{RST}$ , the JTAG/SWD port pins default to their JTAG/SWD configurations. The default configuration includes enabling digital functionality (setting **GPIODEN** to 1), enabling the pull-up resistors (setting **GPIOPUR** to 1), and enabling the alternate hardware function (setting **GPIOAFSEL** to 1) for the PB7 and PC[3:0] JTAG/SWD pins.

It is possible for software to configure these pins as GPIOs after reset by writing 0s to PB7 and PC[3:0] in the **GPIOAFSEL** register. If the user does not require the JTAG/SWD port for debugging or board-level testing, this provides five more GPIOs for use in the design.

Caution – It is possible to create a software sequence that prevents the debugger from connecting to the Stellaris microcontroller. If the program code loaded into flash immediately changes the JTAG pins to their GPIO functionality, the debugger may not have enough time to connect and halt the controller before the JTAG pin functionality switches. This may lock the debugger out of the part. This can be avoided with a software routine that restores JTAG functionality based on an external or software trigger.

The GPIO commit control registers provide a layer of protection against accidental programming of critical hardware peripherals. Protection is currently provided for the five JTAG/SWD pins (PB7 and PC[3:0]). Writes to protected bits of the **GPIO Alternate Function Select (GPIOAFSEL)** register (see page 272) are not committed to storage unless the **GPIO Lock (GPIOLOCK)** register (see page 282) has been unlocked and the appropriate bits of the **GPIO Commit (GPIOCR)** register (see page 283) have been set to 1.

#### Recovering a "Locked" Device

**Note:** The mass erase of the flash memory caused by the below sequence erases the entire flash memory, regardless of the settings in the **Flash Memory Protection Program Enable n** (**FMPPEn**) registers. Performing the sequence below does not affect the nonvolatile registers discussed in "Nonvolatile Register Programming" on page 228.

If software configures any of the JTAG/SWD pins as GPIO and loses the ability to communicate with the debugger, there is a debug sequence that can be used to recover the device. Performing a total of ten JTAG-to-SWD and SWD-to-JTAG switch sequences while holding the device in reset mass erases the flash memory. The sequence to recover the device is:

- 1. Assert and hold the  $\overline{\mathtt{RST}}$  signal.
- **2.** Perform the JTAG-to-SWD switch sequence.
- 3. Perform the SWD-to-JTAG switch sequence.
- **4.** Perform the JTAG-to-SWD switch sequence.
- **5.** Perform the SWD-to-JTAG switch sequence.
- **6.** Perform the JTAG-to-SWD switch sequence.
- **7.** Perform the SWD-to-JTAG switch sequence.
- **8.** Perform the JTAG-to-SWD switch sequence.
- **9.** Perform the SWD-to-JTAG switch sequence.
- **10.** Perform the JTAG-to-SWD switch sequence.

- 11. Perform the SWD-to-JTAG switch sequence.
- **12.** Release the  $\overline{RST}$  signal.
- 13. Wait 400 ms.
- 14. Power-cycle the device.

The JTAG-to-SWD and SWD-to-JTAG switch sequences are described in "ARM Serial Wire Debug (SWD)" on page 157. When performing switch sequences for the purpose of recovering the debug capabilities of the device, only steps 1 and 2 of the switch sequence in the section called "JTAG-to-SWD Switching" on page 157 must be performed.

#### 4.3.4.2 Communication with JTAG/SWD

Because the debug clock and the system clock can be running at different frequencies, care must be taken to maintain reliable communication with the JTAG/SWD interface. In the Capture-DR state, the result of the previous transaction, if any, is returned, together with a 3-bit ACK response. Software should check the ACK response to see if the previous operation has completed before initiating a new transaction. Alternatively, if the system clock is at least 8 times faster than the debug clock (TCK or SWCLK), the previous operation has enough time to complete and the ACK bits do not have to be checked.

## 4.3.4.3 ARM Serial Wire Debug (SWD)

In order to seamlessly integrate the ARM Serial Wire Debug (SWD) functionality, a serial-wire debugger must be able to connect to the Cortex-M3 core without having to perform, or have any knowledge of, JTAG cycles. This is accomplished with a SWD preamble that is issued before the SWD session begins.

The switching preamble used to enable the SWD interface of the SWJ-DP module starts with the TAP controller in the Test-Logic-Reset state. From here, the preamble sequences the TAP controller through the following states: Run Test Idle, Select DR, Select IR, Test Logic Reset, Test Logic Reset, Run Test Idle, Run Test Idle, Select DR, Select IR, Test Logic Reset, Test Logic Reset, Run Test Idle, Select DR, Select IR, and Test Logic Reset states.

Stepping through this sequences of the TAP state machine enables the SWD interface and disables the JTAG interface. For more information on this operation and the SWD interface, see the *ARM® Debug Interface V5 Architecture Specification*.

Because this sequence is a valid series of JTAG operations that could be issued, the ARM JTAG TAP controller is not fully compliant to the *IEEE Standard 1149.1*. This is the only instance where the ARM JTAG TAP controller does not meet full compliance with the specification. Due to the low probability of this sequence occurring during normal operation of the TAP controller, it should not affect normal performance of the JTAG interface.

#### JTAG-to-SWD Switching

To switch the operating mode of the Debug Access Port (DAP) from JTAG to SWD mode, the external debug hardware must send the switching preamble to the device. The 16-bit switch sequence for switching to SWD mode is defined as b1110011110011110, transmitted LSB first. This can also be represented as 16'hE79E when transmitted LSB first. The complete switch sequence should consist of the following transactions on the TCK/SWCLK and TMS/SWDIO signals:

1. Send at least 50 TCK/SWCLK cycles with TMS/SWDIO set to 1. This ensures that both JTAG and SWD are in their reset/idle states.

- 2. Send the 16-bit JTAG-to-SWD switch sequence, 16'hE79E.
- 3. Send at least 50 TCK/SWCLK cycles with TMS/SWDIO set to 1. This ensures that if SWJ-DP was already in SWD mode, before sending the switch sequence, the SWD goes into the line reset state.

#### SWD-to-JTAG Switching

To switch the operating mode of the Debug Access Port (DAP) from SWD to JTAG mode, the external debug hardware must send a switch sequence to the device. The 16-bit switch sequence for switching to JTAG mode is defined as b11100111100111100, transmitted LSB first. This can also be represented as 16'hE73C when transmitted LSB first. The complete switch sequence should consist of the following transactions on the TCK/SWCLK and TMS/SWDIO signals:

- 1. Send at least 50 TCK/SWCLK cycles with TMS/SWDIO set to 1. This ensures that both JTAG and SWD are in their reset/idle states.
- 2. Send the 16-bit SWD-to-JTAG switch sequence, 16'hE73C.
- 3. Send at least 5 TCK/SWCLK cycles with TMS/SWDIO set to 1. This ensures that if SWJ-DP was already in JTAG mode, before sending the switch sequence, the JTAG goes into the Test Logic Reset state.

# 4.4 Initialization and Configuration

After a Power-On-Reset or an external reset ( $\overline{RST}$ ), the JTAG pins are automatically configured for JTAG communication. No user-defined initialization or configuration is needed. However, if the user application changes these pins to their GPIO function, they must be configured back to their JTAG functionality before JTAG communication can be restored. This is done by enabling the five JTAG pins (PB7 and PC[3:0]) for their alternate function using the **GPIOAFSEL** register. In addition to enabling the alternate functions, any other changes to the GPIO pad configurations on the five JTAG pins (PB7 and PC[3:0]) should be reverted to their default settings.

# 4.5 Register Descriptions

There are no APB-accessible registers in the JTAG TAP Controller or Shift Register chains. The registers within the JTAG controller are all accessed serially through the TAP Controller. The registers can be broken down into two main categories: Instruction Registers and Data Registers.

## 4.5.1 Instruction Register (IR)

The JTAG TAP Instruction Register (IR) is a four-bit serial scan chain connected between the JTAG TDI and TDO pins with a parallel load register. When the TAP Controller is placed in the correct states, bits can be shifted into the Instruction Register. Once these bits have been shifted into the chain and updated, they are interpreted as the current instruction. The decode of the Instruction Register bits is shown in Table 4-4 on page 158. A detailed explanation of each instruction, along with its associated Data Register, follows.

**Table 4-4. JTAG Instruction Register Commands** 

IR[3:0]	Instruction	Description
0000		Drives the values preloaded into the Boundary Scan Chain by the SAMPLE/PRELOAD instruction onto the pads.
0001		Drives the values preloaded into the Boundary Scan Chain by the SAMPLE/PRELOAD instruction into the controller.

Table 4-4. JTAG Instruction Register Commands (continued)

IR[3:0]	Instruction	Description
0010	SAMPLE / PRELOAD	Captures the current I/O values and shifts the sampled values out of the Boundary Scan Chain while new preload data is shifted in.
1000	ABORT	Shifts data into the ARM Debug Port Abort Register.
1010	DPACC	Shifts data into and out of the ARM DP Access Register.
1011	APACC	Shifts data into and out of the ARM AC Access Register.
1110	IDCODE	Loads manufacturing information defined by the <i>IEEE Standard 1149.1</i> into the IDCODE chain and shifts it out.
1111	BYPASS	Connects TDI to TDO through a single Shift Register chain.
All Others	Reserved	Defaults to the BYPASS instruction to ensure that ${\tt TDI}$ is always connected to ${\tt TDO}.$

#### 4.5.1.1 EXTEST Instruction

The EXTEST instruction is not associated with its own Data Register chain. The EXTEST instruction uses the data that has been preloaded into the Boundary Scan Data Register using the SAMPLE/PRELOAD instruction. When the EXTEST instruction is present in the Instruction Register, the preloaded data in the Boundary Scan Data Register associated with the outputs and output enables are used to drive the GPIO pads rather than the signals coming from the core. This allows tests to be developed that drive known values out of the controller, which can be used to verify connectivity. While the EXTEST instruction is present in the Instruction Register, the Boundary Scan Data Register can be accessed to sample and shift out the current data and load new data into the Boundary Scan Data Register.

#### 4.5.1.2 INTEST Instruction

The INTEST instruction is not associated with its own Data Register chain. The INTEST instruction uses the data that has been preloaded into the Boundary Scan Data Register using the SAMPLE/PRELOAD instruction. When the INTEST instruction is present in the Instruction Register, the preloaded data in the Boundary Scan Data Register associated with the inputs are used to drive the signals going into the core rather than the signals coming from the GPIO pads. This allows tests to be developed that drive known values into the controller, which can be used for testing. It is important to note that although the  $\overline{\text{RST}}$  input pin is on the Boundary Scan Data Register chain, it is only observable. While the INTEXT instruction is present in the Instruction Register, the Boundary Scan Data Register can be accessed to sample and shift out the current data and load new data into the Boundary Scan Data Register.

### 4.5.1.3 SAMPLE/PRELOAD Instruction

The SAMPLE/PRELOAD instruction connects the Boundary Scan Data Register chain between TDI and TDO. This instruction samples the current state of the pad pins for observation and preloads new test data. Each GPIO pad has an associated input, output, and output enable signal. When the TAP controller enters the Capture DR state during this instruction, the input, output, and output-enable signals to each of the GPIO pads are captured. These samples are serially shifted out of TDO while the TAP controller is in the Shift DR state and can be used for observation or comparison in various tests.

While these samples of the inputs, outputs, and output enables are being shifted out of the Boundary Scan Data Register, new data is being shifted into the Boundary Scan Data Register from TDI. Once the new data has been shifted into the Boundary Scan Data Register, the data is saved in the parallel load registers when the TAP controller enters the Update DR state. This update of the parallel load register preloads data into the Boundary Scan Data Register that is associated with

each input, output, and output enable. This preloaded data can be used with the EXTEST and INTEST instructions to drive data into or out of the controller. Please see "Boundary Scan Data Register" on page 161 for more information.

#### 4.5.1.4 ABORT Instruction

The ABORT instruction connects the associated ABORT Data Register chain between TDI and TDO. This instruction provides read and write access to the ABORT Register of the ARM Debug Access Port (DAP). Shifting the proper data into this Data Register clears various error bits or initiates a DAP abort of a previous request. Please see the "ABORT Data Register" on page 162 for more information.

#### 4.5.1.5 DPACC Instruction

The DPACC instruction connects the associated DPACC Data Register chain between TDI and TDO. This instruction provides read and write access to the DPACC Register of the ARM Debug Access Port (DAP). Shifting the proper data into this register and reading the data output from this register allows read and write access to the ARM debug and status registers. Please see "DPACC Data Register" on page 162 for more information.

### 4.5.1.6 APACC Instruction

The APACC instruction connects the associated APACC Data Register chain between TDI and TDO. This instruction provides read and write access to the APACC Register of the ARM Debug Access Port (DAP). Shifting the proper data into this register and reading the data output from this register allows read and write access to internal components and buses through the Debug Port. Please see "APACC Data Register" on page 162 for more information.

#### 4.5.1.7 IDCODE Instruction

The IDCODE instruction connects the associated IDCODE Data Register chain between <code>TDI</code> and <code>TDO</code>. This instruction provides information on the manufacturer, part number, and version of the ARM core. This information can be used by testing equipment and debuggers to automatically configure their input and output data streams. IDCODE is the default instruction that is loaded into the JTAG Instruction Register when a Power-On-Reset (POR) is asserted, <code>TRST</code> is asserted, or the Test-Logic-Reset state is entered. Please see "IDCODE Data Register" on page 161 for more information.

#### 4.5.1.8 BYPASS Instruction

The BYPASS instruction connects the associated BYPASS Data Register chain between TDI and TDO. This instruction is used to create a minimum length serial path between the TDI and TDO ports. The BYPASS Data Register is a single-bit shift register. This instruction improves test efficiency by allowing components that are not needed for a specific test to be bypassed in the JTAG scan chain by loading them with the BYPASS instruction. Please see "BYPASS Data Register" on page 161 for more information.

## 4.5.2 Data Registers

The JTAG module contains six Data Registers. These include: IDCODE, BYPASS, Boundary Scan, APACC, DPACC, and ABORT serial Data Register chains. Each of these Data Registers is discussed in the following sections.

### 4.5.2.1 IDCODE Data Register

The format for the 32-bit IDCODE Data Register defined by the *IEEE Standard 1149.1* is shown in Figure 4-3 on page 161. The standard requires that every JTAG-compliant device implement either the IDCODE instruction or the BYPASS instruction as the default instruction. The LSB of the IDCODE Data Register is defined to be a 1 to distinguish it from the BYPASS instruction, which has an LSB of 0. This allows auto configuration test tools to determine which instruction is the default instruction.

The major uses of the JTAG port are for manufacturer testing of component assembly, and program development and debug. To facilitate the use of auto-configuration debug tools, the IDCODE instruction outputs a value of 0x3BA0.0477. This allows the debuggers to automatically configure themselves to work correctly with the Cortex-M3 during debug.

Figure 4-3. IDCODE Register Format



## 4.5.2.2 BYPASS Data Register

The format for the 1-bit BYPASS Data Register defined by the *IEEE Standard 1149.1* is shown in Figure 4-4 on page 161. The standard requires that every JTAG-compliant device implement either the BYPASS instruction or the IDCODE instruction as the default instruction. The LSB of the BYPASS Data Register is defined to be a 0 to distinguish it from the IDCODE instruction, which has an LSB of 1. This allows auto configuration test tools to determine which instruction is the default instruction.

Figure 4-4. BYPASS Register Format

### 4.5.2.3 Boundary Scan Data Register

The format of the Boundary Scan Data Register is shown in Figure 4-5 on page 162. Each GPIO pin, starting with a GPIO pin next to the JTAG port pins, is included in the Boundary Scan Data Register. Each GPIO pin has three associated digital signals that are included in the chain. These signals are input, output, and output enable, and are arranged in that order as can be seen in the figure.

When the Boundary Scan Data Register is accessed with the SAMPLE/PRELOAD instruction, the input, output, and output enable from each digital pad are sampled and then shifted out of the chain to be verified. The sampling of these values occurs on the rising edge of <code>TCK</code> in the Capture DR state of the TAP controller. While the sampled data is being shifted out of the Boundary Scan chain in the Shift DR state of the TAP controller, new data can be preloaded into the chain for use with the EXTEST and INTEST instructions. These instructions either force data out of the controller, with the EXTEST instruction, or into the controller, with the INTEST instruction.

## Figure 4-5. Boundary Scan Register Format

## 4.5.2.4 APACC Data Register

The format for the 35-bit APACC Data Register defined by ARM is described in the ARM® Debug Interface V5 Architecture Specification.

## 4.5.2.5 DPACC Data Register

The format for the 35-bit DPACC Data Register defined by ARM is described in the *ARM® Debug Interface V5 Architecture Specification*.

## 4.5.2.6 ABORT Data Register

The format for the 35-bit ABORT Data Register defined by ARM is described in the *ARM® Debug Interface V5 Architecture Specification*.

# 5 System Control

System control determines the overall operation of the device. It provides information about the device, controls the clocking to the core and individual peripherals, and handles reset detection and reporting.

## 5.1 Signal Description

Table 5-1 on page 163 and Table 5-2 on page 163 list the external signals of the System Control module and describe the function of each. The NMI signal is the alternate function for and functions as a GPIO after reset. under commit protection and require a special process to be configured as any alternate function or to subsequently return to the GPIO function, see "Commit Control" on page 258. The column in the table below titled "Pin Assignment" lists the GPIO pin placement for the NMI signal. The AFSEL bit in the **GPIO Alternate Function Select (GPIOAFSEL)** register (page 272) should be set to choose the NMI function. For more information on configuring GPIOs, see "General-Purpose Input/Outputs (GPIOs)" on page 251. The remaining signals (with the word "fixed" in the Pin Assignment column) have a fixed pin assignment and function.

Table 5-1. System Control & Clocks Signals (100LQFP)

Pin Name	Pin Number	Pin Type	Buffer Type <sup>a</sup>	Description
CMOD0	65	I	TTL	CPU Mode bit 0. Input must be set to logic 0 (grounded); other encodings reserved.
CMOD1	76	I	TTL	CPU Mode bit 1. Input must be set to logic 0 (grounded); other encodings reserved.
osc0	48	I	Analog	Main oscillator crystal input or an external clock reference input.
OSC1	49	0	Analog	Main oscillator crystal output. Leave unconnected when using a single-ended clock source.
RST	64	I	TTL	System reset input.

a. The TTL designation indicates the pin has TTL-compatible voltage levels.

Table 5-2. System Control & Clocks Signals (108BGA)

Pin Name	Pin Number	Pin Type	Buffer Type <sup>a</sup>	Description
CMOD0	E11	I	TTL	CPU Mode bit 0. Input must be set to logic 0 (grounded); other encodings reserved.
CMOD1	B10	I	TTL	CPU Mode bit 1. Input must be set to logic 0 (grounded); other encodings reserved.
osc0	L11	I	Analog	Main oscillator crystal input or an external clock reference input.
OSC1	M11	0	Analog	Main oscillator crystal output. Leave unconnected when using a single-ended clock source.
RST	H11	I	TTL	System reset input.

a. The TTL designation indicates the pin has TTL-compatible voltage levels.

# **5.2** Functional Description

The System Control module provides the following capabilities:

■ Device identification (see "Device Identification" on page 164)

- Local control, such as reset (see "Reset Control" on page 164), power (see "Power Control" on page 168) and clock control (see "Clock Control" on page 169)
- System control (Run, Sleep, and Deep-Sleep modes); see "System Control" on page 174

#### 5.2.1 Device Identification

Several read-only registers provide software with information on the microcontroller, such as version, part number, SRAM size, flash size, and other features. See the **DID0**, **DID1**, and **DC0-DC4** registers.

### 5.2.2 Reset Control

This section discusses aspects of hardware functions during reset as well as system software requirements following the reset sequence.

#### 5.2.2.1 CMOD0 and CMOD1 Test-Mode Control Pins

Two pins, CMOD0 and CMOD1, are defined for internal use for testing the microcontroller during manufacture. They have no end-user function and should not be used. The CMOD pins should be connected to ground.

#### 5.2.2.2 Reset Sources

The controller has five sources of reset:

- External reset input pin (RST) assertion; see "External RST Pin" on page 165.
- 2. Power-on reset (POR); see "Power-On Reset (POR)" on page 165.
- 3. Internal brown-out (BOR) detector; see "Brown-Out Reset (BOR)" on page 166.
- Software-initiated reset (with the software reset registers); see "Software Reset" on page 167.
- 5. A watchdog timer reset condition violation; see "Watchdog Timer Reset" on page 167.

Table 5-3 provides a summary of results of the various reset operations.

**Table 5-3. Reset Sources** 

Reset Source	Core Reset?	JTAG Reset?	On-Chip Peripherals Reset?
Power-On Reset	Yes	Yes	Yes
RST	Yes	Pin Config Only	Yes
Brown-Out Reset	Yes	No	Yes
Software System Request Reset <sup>a</sup>	Yes	No	Yes
Software Peripheral Reset	No	No	Yes <sup>b</sup>
Watchdog Reset	Yes	No	Yes

a. By using the SYSRESREQ bit in the ARM Cortex-M3 Application Interrupt and Reset Control (APINT) register

After a reset, the **Reset Cause (RESC)** register is set with the reset cause. The bits in this register are sticky and maintain their state across multiple reset sequences, except when an internal POR is the cause, and then all the other bits in the **RESC** register are cleared except for the POR indicator.

b. Programmable on a module-by-module basis using the Software Reset Control Registers.

### 5.2.2.3 Power-On Reset (POR)

Note: The power-on reset also resets the JTAG controller. An external reset does not.

The internal Power-On Reset (POR) circuit monitors the power supply voltage ( $V_{DD}$ ) and generates a reset signal to all of the internal logic including JTAG when the power supply ramp reaches a threshold value ( $V_{TH}$ ). The microcontroller must be operating within the specified operating parameters when the on-chip power-on reset pulse is complete. The 3.3-V power supply to the microcontroller must reach 3.0 V within 10 msec of  $V_{DD}$  crossing 2.0 V to guarantee proper operation. For applications that require the use of an external reset signal to hold the microcontroller in reset longer than the internal POR, the  $\overline{RST}$  input may be used as discussed in "External  $\overline{RST}$  Pin" on page 165.

The Power-On Reset sequence is as follows:

- 1. The microcontroller waits for internal POR to go inactive.
- 2. The internal reset is released and the core loads from memory the initial stack pointer, the initial program counter, and the first instruction designated by the program counter, and then begins execution.


The internal POR is only active on the initial power-up of the microcontroller. The Power-On Reset timing is shown in Figure 18-6 on page 567.

### 5.2.2.4 External RST Pin

**Note:** It is recommended that the trace for the  $\overline{RST}$  signal must be kept as short as possible. Be sure to place any components connected to the  $\overline{RST}$  signal as close to the microcontroller as possible.

If the application only uses the internal POR circuit, the  $\overline{\text{RST}}$  input must be connected to the power supply  $(V_{DD})$  through an optional pull-up resistor (0 to 100K  $\Omega$ ) as shown in Figure 5-1 on page 165.

Figure 5-1. Basic RST Configuration




 $R_{PU}$  = 0 to 100 k $\Omega$ 

The external reset pin (RST) resets the microcontroller including the core and all the on-chip peripherals except the JTAG TAP controller (see "JTAG Interface" on page 150). The external reset sequence is as follows:

- 1. The external reset pin ( $\overline{RST}$ ) is asserted for the duration specified by  $T_{MIN}$  and then de-asserted (see "Reset" on page 566).
- 2. The internal reset is released and the core loads from memory the initial stack pointer, the initial program counter, and the first instruction designated by the program counter, and then begins execution.

To improve noise immunity and/or to delay reset at power up, the  $\overline{RST}$  input may be connected to an RC network as shown in Figure 5-2 on page 166.

Figure 5-2. External Circuitry to Extend Power-On Reset




 $R_{PU}$  = 1 k $\Omega$  to 100 k $\Omega$ 

 $C_1 = 1 \text{ nF to } 10 \mu\text{F}$ 

If the application requires the use of an external reset switch, Figure 5-3 on page 166 shows the proper circuitry to use.

Figure 5-3. Reset Circuit Controlled by Switch



Typical  $R_{PU} = 10 \text{ k}\Omega$ 

Typical  $R_S = 470 \Omega$ 

 $C_1 = 10 \text{ nF}$ 

The R<sub>PIJ</sub> and C<sub>1</sub> components define the power-on delay.

The external reset timing is shown in Figure 18-5 on page 567.

## 5.2.2.5 Brown-Out Reset (BOR)

A drop in the input voltage resulting in the assertion of the internal brown-out detector can be used to reset the controller. This is initially disabled and may be enabled by software.

The system provides a brown-out detection circuit that triggers if the power supply  $(V_{DD})$  drops below a brown-out threshold voltage  $(V_{BTH})$ . If a brown-out condition is detected, the system may generate a controller interrupt or a system reset.

Brown-out resets are controlled with the **Power-On and Brown-Out Reset Control (PBORCTL)** register. The BORIOR bit in the **PBORCTL** register must be set for a brown-out condition to trigger a reset.

The brown-out reset is equivalent to an assertion of the external  $\overline{\mathtt{RST}}$  input and the reset is held active until the proper  $V_{DD}$  level is restored. The **RESC** register can be examined in the reset interrupt handler to determine if a Brown-Out condition was the cause of the reset, thus allowing software to determine what actions are required to recover.

The internal Brown-Out Reset timing is shown in Figure 18-7 on page 567.

#### 5.2.2.6 Software Reset

Software can reset a specific peripheral or generate a reset to the entire system.

Peripherals can be individually reset by software via three registers that control reset signals to each peripheral (see the **SRCRn** registers). If the bit position corresponding to a peripheral is set and subsequently cleared, the peripheral is reset. The encoding of the reset registers is consistent with the encoding of the clock gating control for peripherals and on-chip functions (see "System Control" on page 174). Note that all reset signals for all clocks of the specified unit are asserted as a result of a software-initiated reset.

The entire system can be reset by software by setting the SYSRESETREQ bit in the Cortex-M3 Application Interrupt and Reset Control register resets the entire system including the core. The software-initiated system reset sequence is as follows:

- **1.** A software system reset is initiated by writing the SYSRESETREQ bit in the ARM Cortex-M3 Application Interrupt and Reset Control register.
- 2. An internal reset is asserted.
- The internal reset is deasserted and the controller loads from memory the initial stack pointer, the initial program counter, and the first instruction designated by the program counter, and then begins execution.

The software-initiated system reset timing is shown in Figure 18-8 on page 568.

## 5.2.2.7 Watchdog Timer Reset

The watchdog timer module's function is to prevent system hangs. The watchdog timer can be configured to generate an interrupt to the controller on its first time-out, and to generate a reset signal on its second time-out.

After the first time-out event, the 32-bit counter is reloaded with the value of the **Watchdog Timer Load (WDTLOAD)** register, and the timer resumes counting down from that value. If the timer counts down to its zero state again before the first time-out interrupt is cleared, and the reset signal has been enabled, the watchdog timer asserts its reset signal to the system. The watchdog timer reset sequence is as follows:

- 1. The watchdog timer times out for the second time without being serviced.
- 2. An internal reset is asserted.
- The internal reset is released and the controller loads from memory the initial stack pointer, the initial program counter, the first instruction designated by the program counter, and begins execution.

The watchdog reset timing is shown in Figure 18-9 on page 568.

## 5.2.3 Power Control

The Stellaris  $^{\otimes}$  microcontroller provides an integrated LDO regulator that is used to provide power to the majority of the controller's internal logic. For power reduction, the LDO regulator provides software a mechanism to adjust the regulated value, in small increments (VSTEP), over the range of 2.25 V to 2.75 V (inclusive)—or 2.5 V  $\pm$  10%. The adjustment is made by changing the value of the VADJ field in the **LDO Power Control (LDOPCTL)** register.

Figure 5-4 on page 169 shows the power architecture.

**Note:** On the printed circuit board, use the LDO output as the source of VDD25 input. Do not use an external regulator to supply the voltage to VDD25. In addition, the LDO requires decoupling capacitors. See "On-Chip Low Drop-Out (LDO) Regulator Characteristics" on page 561.

VDDA must be supplied with 3.3 V, or the microcontroller does not function properly. VDDA is the supply for all of the analog circuitry on the device, including the LDO and the clock circuitry.




Figure 5-4. Power Architecture

## 5.2.4 Clock Control

System control determines the control of clocks in this part.

## 5.2.4.1 Fundamental Clock Sources

There are multiple clock sources for use in the device:

■ Internal Oscillator (IOSC). The internal oscillator is an on-chip clock source. It does not require the use of any external components. The frequency of the internal oscillator is 12 MHz ± 30%.

Applications that do not depend on accurate clock sources may use this clock source to reduce system cost. The internal oscillator is the clock source the device uses during and following POR. If the main oscillator is required, software must enable the main oscillator following reset and allow the main oscillator to stabilize before changing the clock reference.

- Main Oscillator (MOSC). The main oscillator provides a frequency-accurate clock source by one of two means: an external single-ended clock source is connected to the OSC0 input pin, or an external crystal is connected across the OSC0 input and OSC1 output pins. If the PLL is being used, the crystal value must be one of the supported frequencies between 3.579545 MHz through 8.192 MHz (inclusive). If the PLL is not being used, the crystal may be any one of the supported frequencies between 1 MHz and 8.192 MHz. The single-ended clock source range is from DC through the specified speed of the device. The supported crystals are listed in the XTAL bit field in the RCC register (see page 185).
- Internal 30-kHz Oscillator. The internal 30-kHz oscillator is similar to the internal oscillator, except that it provides an operational frequency of 30 kHz ± 50%. It is intended for use during Deep-Sleep power-saving modes. This power-savings mode benefits from reduced internal switching and also allows the main oscillator to be powered down.

The internal system clock (SysClk), is derived from any of the above sources plus two others: the output of the main internal PLL, and the internal oscillator divided by four (3 MHz  $\pm$  30%). The frequency of the PLL clock reference must be in the range of 3.579545 MHz to 8.192 MHz (inclusive). Table 5-4 on page 170 shows how the various clock sources can be used in a system.

	•				
Clock Source	Drive PLL?		Used as SysClk?		
Internal Oscillator (12 MHz)	No	BYPASS = 1	Yes	BYPASS = 1, OSCSRC = 0x1	
Internal Oscillator divide by 4 (3 MHz)	No	BYPASS = 1	Yes	BYPASS = 1, OSCSRC = 0x2	
Main Oscillator	Yes	BYPASS = 0, OSCSRC = 0x0	Yes	BYPASS = 1, OSCSRC = 0x0	
Internal 30-kHz Oscillator	No	BYPASS = 1	Yes	BYPASS = 1. OSCSRC = 0x3	

**Table 5-4. Clock Source Options** 

### 5.2.4.2 Clock Configuration


The Run-Mode Clock Configuration (RCC) and Run-Mode Clock Configuration 2 (RCC2) registers provide control for the system clock. The RCC2 register is provided to extend fields that offer additional encodings over the RCC register. When used, the RCC2 register field values are used by the logic over the corresponding field in the RCC register. In particular, RCC2 provides for a larger assortment of clock configuration options. These registers control the following clock functionality:

- Source of clocks in sleep and deep-sleep modes
- System clock derived from PLL or other clock source
- Enabling/disabling of oscillators and PLL
- Clock divisors
- Crystal input selection

Figure 5-5 on page 171 shows the logic for the main clock tree. The peripheral blocks are driven by the system clock signal and can be individually enabled/disabled. The ADC clock signal is automatically divided down to 16 MHz for proper ADC operation.

**Note:** When the ADC module is in operation, the system clock must be at least 16 MHz.

Figure 5-5. Main Clock Tree



- a. Control provided by RCC register bit/field.
- b. Control provided by RCC register bit/field or RCC2 register bit/field, if overridden with RCC2 register bit USERCC2.
- c. Control provided by RCC2 register bit/field.
- d. Also may be controlled by DSLPCLKCFG when in deep sleep mode.

**Note:** The figure above shows all features available on all Stellaris® Fury-class devices. Not all peripherals may be available on this device.

In the RCC register, the SYSDIV field specifies which divisor is used to generate the system clock from either the PLL output or the oscillator source (depending on how the BYPASS bit in this register is configured). When using the PLL, the VCO frequency of 400 MHz is predivided by 2 before the divisor is applied. Table 5-5 shows how the SYSDIV encoding affects the system clock frequency, depending on whether the PLL is used (BYPASS=0) or another clock source is used (BYPASS=1).

The divisor is equivalent to the SYSDIV encoding plus 1. For a list of possible clock sources, see Table 5-4 on page 170.

Table 5-5. Possible System Clock Frequencies Using the SYSDIV Field

SYSDIV	Divisor	Frequency (BYPASS=0)	Frequency (BYPASS=1)	StellarisWare Parameter <sup>a</sup>
0x0	/1	reserved	Clock source frequency/2	SYSCTL_SYSDIV_1b
0x1	/2	reserved	Clock source frequency/2	SYSCTL_SYSDIV_2
0x2	/3	reserved	Clock source frequency/3	SYSCTL_SYSDIV_3
0x3	/4	reserved	Clock source frequency/4	SYSCTL_SYSDIV_4
0x4	/5	reserved	Clock source frequency/5	SYSCTL_SYSDIV_5
0x5	/6	reserved	Clock source frequency/6	SYSCTL_SYSDIV_6
0x6	/7	reserved	Clock source frequency/7	SYSCTL_SYSDIV_7
0x7	/8	25 MHz	Clock source frequency/8	SYSCTL_SYSDIV_8
0x8	/9	reserved	Clock source frequency/9	SYSCTL_SYSDIV_9
0x9	/10	20 MHz	Clock source frequency/10	SYSCTL_SYSDIV_10
0xA	/11	18.18 MHz	Clock source frequency/11	SYSCTL_SYSDIV_11
0xB	/12	16.67 MHz	Clock source frequency/12	SYSCTL_SYSDIV_12
0xC	/13	15.38 MHz	Clock source frequency/13	SYSCTL_SYSDIV_13
0xD	/14	14.29 MHz	Clock source frequency/14	SYSCTL_SYSDIV_14
0xE	/15	13.33 MHz	Clock source frequency/15	SYSCTL_SYSDIV_15
0xF	/16	12.5 MHz (default)	Clock source frequency/16	SYSCTL_SYSDIV_16

a. This parameter is used in functions such as SysCtlClockSet() in the Stellaris Peripheral Driver Library.

The SYSDIV2 field in the **RCC2** register is 2 bits wider than the SYSDIV field in the **RCC** register so that additional larger divisors up to /64 are possible, allowing a lower system clock frequency for improved Deep Sleep power consumption. When using the PLL, the VCO frequency of 400 MHz is predivided by 2 before the divisor is applied. The divisor is equivalent to the SYSDIV2 encoding plus 1. Table 5-6 shows how the SYSDIV2 encoding affects the system clock frequency, depending on whether the PLL is used (BYPASS2=0) or another clock source is used (BYPASS2=1). For a list of possible clock sources, see Table 5-4 on page 170.

Table 5-6. Examples of Possible System Clock Frequencies Using the SYSDIV2 Field

SYSDIV2	Divisor	Frequency (BYPASS2=0)	Frequency (BYPASS2=1)	StellarisWare Parameter <sup>a</sup>
0x00	/1	reserved	Clock source frequency/2	SYSCTL_SYSDIV_1 <sup>b</sup>
0x01	/2	reserved	Clock source frequency/2	SYSCTL_SYSDIV_2
0x02	/3	reserved	Clock source frequency/3	SYSCTL_SYSDIV_3
0x03	/4	reserved	Clock source frequency/4	SYSCTL_SYSDIV_4
0x04	/5	reserved	Clock source frequency/5	SYSCTL_SYSDIV_5
0x05	/6	reserved	Clock source frequency/6	SYSCTL_SYSDIV_6
0x06	/7	reserved	Clock source frequency/7	SYSCTL_SYSDIV_7
0x07	/8	reserved	Clock source frequency/8	SYSCTL_SYSDIV_8
0x08	/9	reserved	Clock source frequency/9	SYSCTL_SYSDIV_9
0x09	/10	20 MHz	Clock source frequency/10	SYSCTL_SYSDIV_10

b. SYSCTL\_SYSDIV\_1 does not set the USESYSDIV bit. As a result, using this parameter without enabling the PLL results in the system clock having the same frequency as the clock source.

Table 5-6. Examples of Possible System Clock Frequencies Using the SYSDIV2 Field (continued)

SYSDIV2		Frequency (BYPASS2=0)	Frequency (BYPASS2=1)	StellarisWare Parameter <sup>a</sup>
0x3F	/64	3.125 MHz	Clock source frequency/64	SYSCTL_SYSDIV_64

a. This parameter is used in functions such as SysCtlClockSet() in the Stellaris Peripheral Driver Library.

## 5.2.4.3 Crystal Configuration for the Main Oscillator (MOSC)

The main oscillator supports the use of a select number of crystals. If the main oscillator is used by the PLL as a reference clock, the supported range of crystals is 3.579545 to 8.192 MHz, otherwise, the range of supported crystals is 1 to 8.192 MHz.

The XTAL bit in the **RCC** register (see page 185) describes the available crystal choices and default programming values.

Software configures the **RCC** register XTAL field with the crystal number. If the PLL is used in the design, the XTAL field value is internally translated to the PLL settings.

### 5.2.4.4 Main PLL Frequency Configuration

The main PLL is disabled by default during power-on reset and is enabled later by software if required. Software specifies the output divisor to set the system clock frequency, and enables the main PLL to drive the output. The PLL operates at 400 MHz, but is divided by two prior to the application of the output divisor.

If the main oscillator provides the clock reference to the main PLL, the translation provided by hardware and used to program the PLL is available for software in the **XTAL** to **PLL Translation** (**PLLCFG**) register (see page 189). The internal translation provides a translation within  $\pm$  1% of the targeted PLL VCO frequency. Table 18-9 on page 564 shows the actual PLL frequency and error for a given crystal choice.

The Crystal Value field (XTAL) in the **Run-Mode Clock Configuration (RCC)** register (see page 185) describes the available crystal choices and default programming of the **PLLCFG** register. Any time the XTAL field changes, the new settings are translated and the internal PLL settings are updated.

#### 5.2.4.5 PLL Modes

The PLL has two modes of operation: Normal and Power-Down

- Normal: The PLL multiplies the input clock reference and drives the output.
- Power-Down: Most of the PLL internal circuitry is disabled and the PLL does not drive the output.

The modes are programmed using the RCC/RCC2 register fields (see page 185 and page 190).

## 5.2.4.6 PLL Operation

If a PLL configuration is changed, the PLL output frequency is unstable until it reconverges (relocks) to the new setting. The time between the configuration change and relock is T<sub>READY</sub> (see Table 18-8 on page 563). During the relock time, the affected PLL is not usable as a clock reference.

PLL is changed by one of the following:

b. SYSCTL\_SYSDIV\_1 does not set the USESYSDIV bit. As a result, using this parameter without enabling the PLL results in the system clock having the same frequency as the clock source.

- Change to the XTAL value in the RCC register—writes of the same value do not cause a relock.
- Change in the PLL from Power-Down to Normal mode.

A counter is defined to measure the  $T_{READY}$  requirement. The counter is clocked by the main oscillator. The range of the main oscillator has been taken into account and the down counter is set to 0x1200 (that is, ~600  $\mu$ s at an 8.192 MHz external oscillator clock). Hardware is provided to keep the PLL from being used as a system clock until the  $T_{READY}$  condition is met after one of the two changes above. It is the user's responsibility to have a stable clock source (like the main oscillator) before the **RCC/RCC2** register is switched to use the PLL.

If the main PLL is enabled and the system clock is switched to use the PLL in one step, the system control hardware continues to clock the controller from the oscillator selected by the RCC/RCC2 register until the main PLL is stable (T<sub>READY</sub> time met), after which it changes to the PLL. Software can use many methods to ensure that the system is clocked from the main PLL, including periodically polling the PLLLRIS bit in the Raw Interrupt Status (RIS) register, and enabling the PLL Lock interrupt.

## 5.2.5 System Control

For power-savings purposes, the **RCGCn**, **SCGCn**, and **DCGCn** registers control the clock gating logic for each peripheral or block in the system while the controller is in Run, Sleep, and Deep-Sleep mode, respectively.

There are four levels of operation for the device defined as:

- Run Mode. In Run mode, the controller actively executes code. Run mode provides normal operation of the processor and all of the peripherals that are currently enabled by the RCGCn registers. The system clock can be any of the available clock sources including the PLL.
- Sleep Mode. In Sleep mode, the clock frequency of the active peripherals is unchanged, but the processor and the memory subsystem are not clocked and therefore no longer execute code. Sleep mode is entered by the Cortex-M3 core executing a WFI(Wait for Interrupt) instruction. Any properly configured interrupt event in the system will bring the processor back into Run mode. See "Power Management" on page 81 for more details.
  - Peripherals are clocked that are enabled in the **SCGCn** register when auto-clock gating is enabled (see the **RCC** register) or the **RCGCn** register when the auto-clock gating is disabled. The system clock has the same source and frequency as that during Run mode.
- Deep-Sleep Mode. In Deep-Sleep mode, the clock frequency of the active peripherals may change (depending on the Run mode clock configuration) in addition to the processor clock being stopped. An interrupt returns the device to Run mode from one of the sleep modes; the sleep modes are entered on request from the code. Deep-Sleep mode is entered by first writing the Deep Sleep Enable bit in the ARM Cortex-M3 NVIC system control register and then executing a WFI instruction. Any properly configured interrupt event in the system will bring the processor back into Run mode. See "Power Management" on page 81 for more details.

The Cortex-M3 processor core and the memory subsystem are not clocked. Peripherals are clocked that are enabled in the **DCGCn** register when auto-clock gating is enabled (see the **RCC** register) or the **RCGCn** register when auto-clock gating is disabled. The system clock source is the main oscillator by default or the internal oscillator specified in the **DSLPCLKCFG** register if one is enabled. When the **DSLPCLKCFG** register is used, the internal oscillator is powered up, if necessary, and the main oscillator is powered down. If the PLL is running at the time of the WFI instruction, hardware will power the PLL down and override the SYSDIV field of the active

RCC/RCC2 register, to be determined by the DSDIVORIDE setting in the **DSLPCLKCFG** register, up to /16 or /64 respectively. When the Deep-Sleep exit event occurs, hardware brings the system clock back to the source and frequency it had at the onset of Deep-Sleep mode before enabling the clocks that had been stopped during the Deep-Sleep duration.

Caution – If the Cortex-M3 Debug Access Port (DAP) has been enabled, and the device wakes from a low power sleep or deep-sleep mode, the core may start executing code before all clocks to peripherals have been restored to their run mode configuration. The DAP is usually enabled by software tools accessing the JTAG or SWD interface when debugging or flash programming. If this condition occurs, a Hard Fault is triggered when software accesses a peripheral with an invalid clock.

A software delay loop can be used at the beginning of the interrupt routine that is used to wake up a system from a WFI (Wait For Interrupt) instruction. This stalls the execution of any code that accesses a peripheral register that might cause a fault. This loop can be removed for production software as the DAP is most likely not enabled during normal execution.

Because the DAP is disabled by default (power on reset), the user can also power-cycle the device. The DAP is not enabled unless it is enabled through the JTAG or SWD interface.

# 5.3 Initialization and Configuration

The PLL is configured using direct register writes to the RCC/RCC2 register. If the RCC2 register is being used, the USERCC2 bit must be set and the appropriate RCC2 bit/field is used. The steps required to successfully change the PLL-based system clock are:

- 1. Bypass the PLL and system clock divider by setting the BYPASS bit and clearing the USESYS bit in the RCC register. This configures the system to run off a "raw" clock source and allows for the new PLL configuration to be validated before switching the system clock to the PLL.
- 2. Select the crystal value (XTAL) and oscillator source (OSCSRC), and clear the PWRDN bit in RCC/RCC2. Setting the XTAL field automatically pulls valid PLL configuration data for the appropriate crystal, and clearing the PWRDN bit powers and enables the PLL and its output.
- **3.** Select the desired system divider (SYSDIV) in RCC/RCC2 and set the USESYS bit in RCC. The SYSDIV field determines the system frequency for the microcontroller.
- 4. Wait for the PLL to lock by polling the PLLLRIS bit in the Raw Interrupt Status (RIS) register.
- **5.** Enable use of the PLL by clearing the BYPASS bit in RCC/RCC2.

# 5.4 Register Map

Table 5-7 on page 175 lists the System Control registers, grouped by function. The offset listed is a hexadecimal increment to the register's address, relative to the System Control base address of 0x400F.E000.

**Note:** Spaces in the System Control register space that are not used are reserved for future or internal use. Software should not modify any reserved memory address.

Table 5-7. System Control Register Map

Offset	Name	Туре	Reset	Description	See page
0x000	DID0	RO	-	Device Identification 0	177

Table 5-7. System Control Register Map (continued)

Offset	Name	Туре	Reset	Description	See page
0x004	DID1	RO	-	Device Identification 1	193
0x008	DC0	RO	0x007F.002F	Device Capabilities 0	195
0x010	DC1	RO	0x0001.71BF	Device Capabilities 1	196
0x014	DC2	RO	0x0307.0011	Device Capabilities 2	198
0x018	DC3	RO	0x8F03.0FC0	Device Capabilities 3	200
0x01C	DC4	RO	0x5000.007F	Device Capabilities 4	202
0x030	PBORCTL	R/W	0x0000.7FFD	Brown-Out Reset Control	179
0x034	LDOPCTL	R/W	0x0000.0000	LDO Power Control	180
0x040	SRCR0	R/W	0x00000000	Software Reset Control 0	222
0x044	SRCR1	R/W	0x00000000	Software Reset Control 1	223
0x048	SRCR2	R/W	0x00000000	Software Reset Control 2	224
0x050	RIS	RO	0x0000.0000	Raw Interrupt Status	181
0x054	IMC	R/W	0x0000.0000	Interrupt Mask Control	182
0x058	MISC	R/W1C	0x0000.0000	Masked Interrupt Status and Clear	183
0x05C	RESC	R/W	-	Reset Cause	184
0x060	RCC	R/W	0x0780.3AD1	Run-Mode Clock Configuration	185
0x064	PLLCFG	RO	-	XTAL to PLL Translation	189
0x070	RCC2	R/W	0x0780.2810	Run-Mode Clock Configuration 2	190
0x100	RCGC0	R/W	0x00000040	Run Mode Clock Gating Control Register 0	204
0x104	RCGC1	R/W	0x00000000	Run Mode Clock Gating Control Register 1	210
0x108	RCGC2	R/W	0x00000000	Run Mode Clock Gating Control Register 2	216
0x110	SCGC0	R/W	0x00000040	Sleep Mode Clock Gating Control Register 0	206
0x114	SCGC1	R/W	0x00000000	Sleep Mode Clock Gating Control Register 1	212
0x118	SCGC2	R/W	0x00000000	Sleep Mode Clock Gating Control Register 2	218
0x120	DCGC0	R/W	0x00000040	Deep Sleep Mode Clock Gating Control Register 0	208
0x124	DCGC1	R/W	0x00000000	Deep Sleep Mode Clock Gating Control Register 1	214
0x128	DCGC2	R/W	0x00000000	Deep Sleep Mode Clock Gating Control Register 2	220
0x144	DSLPCLKCFG	R/W	0x0780.0000	Deep Sleep Clock Configuration	192

# 5.5 Register Descriptions


All addresses given are relative to the System Control base address of 0x400F.E000.

## Register 1: Device Identification 0 (DID0), offset 0x000

This register identifies the version of the microcontroller. Each microcontroller is uniquely identified by the combined values of the CLASS field in the **DID0** register and the PARTNO field in the **DID1** register.

Device Identification 0 (DID0)

Base 0x400F.E000 Offset 0x000 Type RO, reset -



Bit/Field	Name	Type	Reset	Description
31	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
30:28	VER	RO	0x1	DID0 Version
				This field defines the $\textbf{DID0}$ register format version. The version number is numeric. The value of the $\mathtt{VER}$ field is encoded as follows:
				Value Description
				0x1 Second version of the <b>DID0</b> register format.
27:24	reserved	RO	0x0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
23:16	CLASS	RO	0x1	Device Class

The CLASS field value identifies the internal design from which all mask sets are generated for all devices in a particular product line. The CLASS field value is changed for new product lines, for changes in fab process (for example, a remap or shrink), or any case where the MAJOR OF MINOR fields require differentiation from prior devices. The value of the CLASS field is encoded as follows (all other encodings are reserved):

Value Description

0x1 Stellaris® Fury-class devices.

Bit/Field	Name	Туре	Reset	Description
15:8	MAJOR	RO	-	Major Revision  This field specifies the major revision number of the device. The major revision reflects changes to base layers of the design. The major revision number is indicated in the part number as a letter (A for first revision, B for second, and so on). This field is encoded as follows:
				Value Description
				0x0 Revision A (initial device)
				0x1 Revision B (first base layer revision)
				0x2 Revision C (second base layer revision)
				and so on.
7:0	MINOR	RO	-	Minor Revision
				This field specifies the minor revision number of the device. The minor revision reflects changes to the metal layers of the design. The ${\tt MINOR}$ field value is reset when the ${\tt MAJOR}$ field is changed. This field is numeric and is encoded as follows:
				Value Description
				0x0 Initial device, or a major revision update.
				0x1 First metal layer change.
				0x2 Second metal layer change.
				and so on.


## Register 2: Brown-Out Reset Control (PBORCTL), offset 0x030

This register is responsible for controlling reset conditions after initial power-on reset.

## Brown-Out Reset Control (PBORCTL)

Base 0x400F.E000

Offset 0x030 Type R/W, reset 0x0000.7FFD



Bit/Field	Name	Type	Reset	Description
31:2	reserved	RO	0x0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
1	BORIOR	R/W	0	BOR Interrupt or Reset
				This bit controls how a BOR event is signaled to the controller. If set, a reset is signaled. Otherwise, an interrupt is signaled.
0	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.


# Register 3: LDO Power Control (LDOPCTL), offset 0x034

The  $\mathtt{VADJ}$  field in this register adjusts the on-chip output voltage ( $\mathsf{V}_{\mathsf{OUT}}$ ).

## LDO Power Control (LDOPCTL)

Base 0x400F.E000 Offset 0x034

Type R/W, reset 0x0000.0000



Bit/Field	Name	Type	Reset	Description
31:6	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
5:0	VADJ	R/W	0x0	LDO Output Voltage

This field sets the on-chip output voltage. The programming values for the  $\mathtt{VADJ}$  field are provided below.

Value	$V_{OUT}(V)$
0x00	2.50
0x01	2.45
0x02	2.40
0x03	2.35
0x04	2.30
0x05	2.25
0x06-0x3F	Reserved
0x1B	2.75
0x1C	2.70
0x1D	2.65
0x1E	2.60
0x1F	2.55


## Register 4: Raw Interrupt Status (RIS), offset 0x050

Central location for system control raw interrupts. These are set and cleared by hardware.

Raw Interrupt Status (RIS)

Base 0x400F.E000 Offset 0x050

Type RO, reset 0x0000.0000



Bit/Field	Name	Туре	Reset	Description
31:7	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
6	PLLLRIS	RO	0	PLL Lock Raw Interrupt Status
				This bit is set when the PLL T <sub>READY</sub> Timer asserts.
5:2	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
1	BORRIS	RO	0	Brown-Out Reset Raw Interrupt Status
				This bit is the raw interrupt status for any brown-out conditions. If set, a brown-out condition is currently active. This is an unregistered signal from the brown-out detection circuit. An interrupt is reported if the BORIM bit in the <b>IMC</b> register is set and the BORIOR bit in the <b>PBORCTL</b> register is cleared.
0	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.


## Register 5: Interrupt Mask Control (IMC), offset 0x054

Central location for system control interrupt masks.

#### Interrupt Mask Control (IMC)

Base 0x400F.E000

Offset 0x054 Type R/W, reset 0x0000.0000



Bit/Field	Name	Туре	Reset	Description
31:7	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
6	PLLLIM	R/W	0	PLL Lock Interrupt Mask
				This bit specifies whether a PLL Lock interrupt is promoted to a controller interrupt. If set, an interrupt is generated if PLLLRIS in <b>RIS</b> is set; otherwise, an interrupt is not generated.
5:2	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
1	BORIM	R/W	0	Brown-Out Reset Interrupt Mask
				This bit specifies whether a brown-out condition is promoted to a controller interrupt. If set, an interrupt is generated if BORRIS is set; otherwise, an interrupt is not generated.
0	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.


## Register 6: Masked Interrupt Status and Clear (MISC), offset 0x058

On a read, this register gives the current masked status value of the corresponding interrupt. All of the bits are R/W1C and this action also clears the corresponding raw interrupt bit in the RIS register (see page 181).

#### Masked Interrupt Status and Clear (MISC)

Base 0x400F.E000

Offset 0x058
Type R/W1C, reset 0x0000.0000




Bit/Field	Name	Туре	Reset	Description
31:7	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
6	PLLLMIS	R/W1C	0	PLL Lock Masked Interrupt Status
				This bit is set when the PLL $T_{READY}$ timer asserts. The interrupt is cleared by writing a 1 to this bit.
5:2	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
1	BORMIS	R/W1C	0	BOR Masked Interrupt Status
				The ${\tt BORMIS}$ is simply the ${\tt BORRIS}$ ANDed with the mask value, ${\tt BORIM}.$
0	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.

## Register 7: Reset Cause (RESC), offset 0x05C

This register is set with the reset cause after reset. The bits in this register are sticky and maintain their state across multiple reset sequences, except when an power-on reset is the cause, in which case, all bits other than POR in the **RESC** register are cleared.

#### Reset Cause (RESC)

Base 0x400F.E000 Offset 0x05C Type R/W, reset -



Bit/Field	Name	Туре	Reset	Description
31:5	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
4	sw	R/W	-	Software Reset When set, indicates a software reset is the cause of the reset event.
3	WDT	R/W	-	Watchdog Timer Reset When set, indicates a watchdog reset is the cause of the reset event.
2	BOR	R/W	-	Brown-Out Reset When set, indicates a brown-out reset is the cause of the reset event.
1	POR	R/W	-	Power-On Reset When set, indicates a power-on reset is the cause of the reset event.
0	EXT	R/W	-	External Reset When set, indicates an external reset ( $\overline{\tt RST}$ assertion) is the cause of the reset event.


## Register 8: Run-Mode Clock Configuration (RCC), offset 0x060

This register is defined to provide source control and frequency speed.

Run-Mode Clock Configuration (RCC)

Base 0x400F.E000 Offset 0x060

Type R/W, reset 0x0780.3AD1



Bit/Field	Name	Туре	Reset	Description
31:28	reserved	RO	0x0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
27	ACG	R/W	0	Auto Clock Gating
				This bit specifies whether the system uses the Sleep-Mode Clock Gating Control (SCGCn) registers and Deep-Sleep-Mode Clock Gating Control (DCGCn) registers if the controller enters a Sleep or Deep-Sleep mode (respectively). If set, the SCGCn or DCGCn registers are used to control the clocks distributed to the peripherals when the controller is in a sleep mode. Otherwise, the Run-Mode Clock Gating Control (RCGCn) registers are used when the controller enters a sleep mode.
				The <b>RCGCn</b> registers are always used to control the clocks in Run mode.
				This allows peripherals to consume less power when the controller is in a sleep mode and the peripheral is unused.
26:23	SYSDIV	R/W	0xF	System Clock Divisor
				Specifies which divisor is used to generate the system clock from either the PLL output or the oscillator source (depending on how the BYPASS bit in this register is configured). See Table 5-5 on page 172 for bit encodings.
				If the SYSDIV value is less than MINSYSDIV (see page 196), and the PLL is being used, then the MINSYSDIV value is used as the divisor.
				If the PLL is not being used, the <code>SYSDIV</code> value can be less than <code>MINSYSDIV</code> .
22	USESYSDIV	R/W	0	Enable System Clock Divider
				Use the system clock divider as the source for the system clock. The system clock divider is forced to be used when the PLL is selected as the source.

November 18, 2011 185

SYSDIV field in this register.

If the USERCC2 bit in the RCC2 register is set, then the SYSDIV2 field in the RCC2 register is used as the system clock divider rather than the

Bit/Field	Name	Туре	Reset	Description
21:14	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
13	PWRDN	R/W	1	PLL Power Down
				This bit connects to the PLL PWRDN input. The reset value of 1 powers down the PLL.
12	reserved	RO	1	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
11	BYPASS	R/W	1	PLL Bypass
				Chooses whether the system clock is derived from the PLL output or the OSC source. If set, the clock that drives the system is the OSC source. Otherwise, the clock that drives the system is the PLL output clock divided by the system divider.
				See Table 5-5 on page 172 for programming guidelines.
				Note: The ADC must be clocked from the PLL or directly from a 14-MHz to 18-MHz clock source to operate properly. While the ADC works in a 14-18 MHz range, to maintain a 1 M sample/second rate, the ADC must be provided a 16-MHz clock source.
10	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.

Bit/Field	Name	Туре	Reset	Description
9:6	XTAL	R/W	0xB	Crystal Value  This field specifies the crystal value attached to the main oscillator. The encoding for this field is provided below. Depending on the crystal used, the PLL frequency may not be exactly 400 MHz (see Table 18-9 on page 564 for more information).
				Value Crystal Frequency (MHz) Not Crystal Frequency (MHz) Using Using the PLL the PLL
				0x0 1.000 reserved
				0x1 1.8432 reserved
				0x2 2.000 reserved
				0x3 2.4576 reserved
				0x4 3.579545 MHz
				0x5 3.6864 MHz
				0x6 4 MHz
				0x7 4.096 MHz
				0x8 4.9152 MHz
				0x9 5 MHz
				0xA 5.12 MHz
				0xB 6 MHz (reset value)
				0xC 6.144 MHz
				0xD 7.3728 MHz
				0xE 8 MHz
				0xF 8.192 MHz
5:4	OSCSRC	R/W	0x1	Oscillator Source
				Selects the input source for the OSC. The values are:
				Value Input Source
				0x0 MOSC
				Main oscillator
				0x1 IOSC
				Internal oscillator (default)
				0x2 IOSC/4
				Internal oscillator / 4  0x3 30 kHz
				30-KHz internal oscillator
				For additional oscillator sources, see the RCC2 register.
3:2	reserved	RO	0x0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
1	IOSCDIS	R/W	0	Internal Oscillator Disable
·			-	0: Internal oscillator (IOSC) is enabled.
				1: Internal oscillator is disabled.

Bit/Field	Name	Type	Reset	Description
0	MOSCDIS	R/W	1	Main Oscillator Disable 0: Main oscillator is enabled.
				1. Main oscillator is disabled (default)


## Register 9: XTAL to PLL Translation (PLLCFG), offset 0x064

This register provides a means of translating external crystal frequencies into the appropriate PLL settings. This register is initialized during the reset sequence and updated anytime that the XTAL field changes in the **Run-Mode Clock Configuration (RCC)** register (see page 185).

The PLL frequency is calculated using the PLLCFG field values, as follows:

#### XTAL to PLL Translation (PLLCFG)

Base 0x400F.E000 Offset 0x064 Type RO, reset -



Bit/Field	Name	Type	Reset	Description
31:14	reserved	RO	0x0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
13:5	F	RO	-	PLL F Value This field specifies the value supplied to the PLL's F input.
4:0	R	RO	-	PLL R Value

This field specifies the value supplied to the PLL's R input.

## Register 10: Run-Mode Clock Configuration 2 (RCC2), offset 0x070

This register overrides the RCC equivalent register fields, as shown in Table 5-8, when the USERCC2 bit is set, allowing the extended capabilities of the RCC2 register to be used while also providing a means to be backward-compatible to previous parts. Each RCC2 field that supersedes an RCC field is located at the same LSB bit position; however, some RCC2 fields are larger than the corresponding RCC field.


Table 5-8. RCC2 Fields that Override RCC fields

RCC2 Field	Overrides RCC Field
SYSDIV2, bits[28:23]	SYSDIV, bits[26:23]
PWRDN2, bit[13]	PWRDN, bit[13]
BYPASS2, bit[11]	BYPASS, bit[11]
oscsrc2, bits[6:4]	oscsrc, bits[5:4]

Run-Mode Clock Configuration 2 (RCC2)

Base 0x400F.E000 Offset 0x070

Type R/W, reset 0x0780.2810



Bit/Field	Name	Туре	Reset	Description
31	USERCC2	R/W	0	Use RCC2 When set, overrides the <b>RCC</b> register fields.
30:29	reserved	RO	0x0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
28:23	SYSDIV2	R/W	0x0F	System Clock Divisor
				Specifies which divisor is used to generate the system clock from either the PLL output or the oscillator source (depending on how the BYPASS2 bit is configured). SYSDIV2 is used for the divisor when both the USESYSDIV bit in the RCC register and the USERCC2 bit in this register are set. See Table 5-6 on page 172 for programming guidelines.
22:14	reserved	RO	0x0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
13	PWRDN2	R/W	1	Power-Down PLL
				When set, powers down the PLL.
12	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.

Bit/Field	Name	Туре	Reset	Description
11	BYPASS2	R/W	1	Bypass PLL When set, bypasses the PLL for the clock source. See Table 5-6 on page 172 for programming guidelines.
10:7	reserved	RO	0x0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
6:4	OSCSRC2	R/W	0x1	Oscillator Source Selects the input source for the OSC. The values are:
				Value Description  0x0 MOSC     Main oscillator  0x1 IOSC     Internal oscillator  0x2 IOSC/4     Internal oscillator / 4  0x3 30 kHz     30-kHz internal oscillator  0x4 Reserved  0x5 Reserved  0x6 Reserved  0x7 Reserved
3:0	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.


## Register 11: Deep Sleep Clock Configuration (DSLPCLKCFG), offset 0x144

This register provides configuration information for the hardware control of Deep Sleep Mode.

Deep Sleep Clock Configuration (DSLPCLKCFG)

Base 0x400F.E000 Offset 0x144

Type R/W, reset 0x0780.0000




Bit/Field	Name	Type	Reset	Description
31:29	reserved	RO	0x0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
28:23	DSDIVORIDE	R/W	0x0F	Divider Field Override
				6-bit system divider field to override when Deep-Sleep occurs with PLL running.
22:7	reserved	RO	0x0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
6:4	DSOSCSRC	R/W	0x0	Clock Source
				Specifies the clock source during Deep-Sleep mode.
				Value Description
				0x0 MOSC
				Use main oscillator as source.
				0x1 IOSC
				Use internal 12-MHz oscillator as source.
				0x2 Reserved
				0x3 30 kHz
				Use 30-kHz internal oscillator as source.
				0x4 Reserved
				0x5 Reserved
				0x6 Reserved
				0x7 Reserved
3:0	reserved	RO	0x0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.

## Register 12: Device Identification 1 (DID1), offset 0x004

This register identifies the device family, part number, temperature range, pin count, and package type. Each microcontroller is uniquely identified by the combined values of the CLASS field in the **DID0** register and the PARTNO field in the **DID1** register.

Device Identification 1 (DID1)

Base 0x400F.E000 Offset 0x004 Type RO, reset -



Bit/Field	Name	Туре	Reset	Description
31:28	VER	RO	0x1	DID1 Version
				This field defines the <b>DID1</b> register format version. The version number is numeric. The value of the $\mathtt{VER}$ field is encoded as follows (all other encodings are reserved):
				Value Description
				0x1 Second version of the <b>DID1</b> register format.
27:24	FAM	RO	0x0	Family
				This field provides the family identification of the device within the Luminary Micro product portfolio. The value is encoded as follows (all other encodings are reserved):
				Value Description
				0x0 Stellaris family of microcontollers, that is, all devices with external part numbers starting with LM3S.
23:16	PARTNO	RO	0x82	Part Number
				This field provides the part number of the device within the family. The value is encoded as follows (all other encodings are reserved):
				Value Description

Value Description 0x82 LM3S6422

15:13 PINCOUNT RO 0x2 Package Pin Count

This field specifies the number of pins on the device package. The value is encoded as follows (all other encodings are reserved):

Value Description

0x2 100-pin or 108-ball package

Bit/Field	Name	Туре	Reset	Description
12:8	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
7:5	TEMP	RO	-	Temperature Range
				This field specifies the temperature rating of the device. The value is encoded as follows (all other encodings are reserved):
				Value Description
				0x0 Commercial temperature range (0°C to 70°C)
				0x1 Industrial temperature range (-40°C to 85°C)
				0x2 Extended temperature range (-40°C to 105°C)
4:3	PKG	RO	-	Package Type
				This field specifies the package type. The value is encoded as follows (all other encodings are reserved):
				Value Description
				0x0 SOIC package
				0x1 LQFP package
				0x2 BGA package
2	ROHS	RO	1	RoHS-Compliance
				This bit specifies whether the device is RoHS-compliant. A 1 indicates the part is RoHS-compliant.
1:0	QUAL	RO	-	Qualification Status
				This field specifies the qualification status of the device. The value is encoded as follows (all other encodings are reserved):
				Value Description
				0x0 Engineering Sample (unqualified)
				0x1 Pilot Production (unqualified)
				0x2 Fully Qualified


## Register 13: Device Capabilities 0 (DC0), offset 0x008

This register is predefined by the part and can be used to verify features.

Device Capabilities 0 (DC0)

Base 0x400F.E000 Offset 0x008

Type RO, reset 0x007F.002F



Bit/Field	Name	Type	Reset	Description
31:16	SRAMSZ	RO	0x007F	SRAM Size Indicates the size of the on-chip SRAM memory.  Value Description 0x007F 32 KB of SRAM
15:0	FLASHSZ	RO	0x002F	Flash Size

Indicates the size of the on-chip flash memory.

Value Description

0x002F 96 KB of Flash

## Register 14: Device Capabilities 1 (DC1), offset 0x010

This register provides a list of features available in the system. The Stellaris family uses this register format to indicate the availability of the following family features in the specific device: CANs, PWM, ADC, Watchdog timer, Hibernation module, and debug capabilities. This register also indicates the maximum clock frequency and maximum ADC sample rate. The format of this register is consistent with the RCGC0, SCGC0, and DCGC0 clock control registers and the SRCR0 software reset control register.

When set, indicates that the Cortex-M3 Memory Protection Unit (MPU) module is present. See the "Cortex-M3 Peripherals" chapter in the

Stellaris Data Sheet for details on the MPU.

#### Device Capabilities 1 (DC1)

Base 0x400F.E000 Offset 0x010

Type RO, reset 0x0001.71BF

	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16
								reserved							'	ADC
Type Reset	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 1
	15	14	13	12	11	10	9	8	7	6	5	4	3	2	1	0
	1		YSDIV	1		rved	MAXAE		MPU	reserved	TEMPSNS	PLL	WDT	swo	SWD	JTAG
Туре	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO
Reset	0	1	1	1	0	0	0	1	1	0	1	1	1	1	1	1
E	Bit/Field		Nam	ne	Ту	ре	Reset	Des	cription							
	31:17		reserv	ved	R	RO					rely on th					
											ure produ ead-mod				ed bit sh	nould be
	16		ADO	С	R	0	1	ADO	C Module	Presen	t					
								When set, indicates that the ADC module is preser								
	15:12		MINSY	SDIV	R	RO		Sys	System Clock Divider							
								hard	dware-de	penden	er value fo t. See the using the	RCC re	egister fo			
								Valı	ue Desc	ription						
								0x7	Spec	ifies a 2	5-MHz clo	ock with	a PLL c	livider of	8.	
	11:10		reserv	ved	R	RO		com	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should preserved across a read-modify-write operation.							
	9:8		MAXAD	CSPD	R	0	0x1	Max	ADC S	peed						
								Indi	cates the	maxim	um rate a	t which	the ADC	sample	s data.	
								Valu	ue Desc	ription						
								0x1	250k	sample	s/second					
	7		MP	U	R	0	1	MPI	J Preser	nt						
	•			-		-	•							_		

Bit/Field	Name	Туре	Reset	Description
6	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
5	TEMPSNS	RO	1	Temp Sensor Present When set, indicates that the on-chip temperature sensor is present.
4	PLL	RO	1	PLL Present When set, indicates that the on-chip Phase Locked Loop (PLL) is present.
3	WDT	RO	1	Watchdog Timer Present When set, indicates that a watchdog timer is present.
2	swo	RO	1	SWO Trace Port Present When set, indicates that the Serial Wire Output (SWO) trace port is present.
1	SWD	RO	1	SWD Present When set, indicates that the Serial Wire Debugger (SWD) is present.
0	JTAG	RO	1	JTAG Present When set, indicates that the JTAG debugger interface is present.

## Register 15: Device Capabilities 2 (DC2), offset 0x014

This register provides a list of features available in the system. The Stellaris family uses this register format to indicate the availability of the following family features in the specific device: Analog Comparators, General-Purpose Timers, I2Cs, QEIs, SSIs, and UARTs. The format of this register is consistent with the **RCGC1**, **SCGC1**, and **DCGC1** clock control registers and the **SRCR1** software reset control register.

23

24

#### Device Capabilities 2 (DC2)

Base 0x400F.E000 Offset 0x014

Type RO, reset 0x0307.0011

		1	rese	rved			COMP1	COMP0		ı	reserved	' '		TIMER2	TIMER1	TIMER0
Type Reset	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 1	RO 1	RO 0	RO 0	RO 0	RO 0	RO 0	RO 1	RO 1	RO 1
	15	14	13	12	11	10	9	8	7	6	5	4	3	2	1	0
		ı	1 1			reserved	ı			ı	ı	SSI0		reserved		UART0
Type Reset	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 1	RO 0	RO 0	RO 0	RO 1
110001	Ü	Ü	Ü	Ü	Ü	Ü	Ü	Ü	Ü	Ü	Ü	•	Ü	Ü	Ü	•
E	Bit/Field		Nam	e	Ty	ре	Reset	Des	cription							
	31:26		reserv	ed .	R	0	0	com	patibility	with fut	ure produ	ne value ucts, the lify-write	value of	a reserv		
	25		COM	D1	R	$\circ$	1				1 Presen		opo.aa.			
	25		COM	r i	IX.	O	'		Ū	•		og comp	arator 1	is prese	nt.	
	24		COM	P0	R	0	1	Ana	log Com	parator	0 Presen	t				
									Ū	•		og comp	arator 0	is prese	nt.	
	23:19		reserv	served RO		0	0	com	Software should not rely on the value of a reserved bit. To procompatibility with future products, the value of a reserved bit spreserved across a read-modify-write operation.							
	18		TIME	R2	R	0	1		er 2 Pres en set, in		that Gen	eral-Purp	oose Tin	ner modu	ıle 2 is p	resent.
	17		TIME	R1	R	0	1	Time	er 1 Pres	sent						
								Whe	en set, in	dicates	that Gen	eral-Purp	oose Tin	ner modu	ıle 1 is p	resent.
	16		TIME	R0	R	0	1	Time	er 0 Pres	sent						
								Whe	en set, in	dicates	that Gen	eral-Purp	oose Tin	ner modu	ıle 0 is p	resent.
	15:5		reserv	ed .	R	0	0	com	patibility	with fut	ure produ	ne value ucts, the lify-write	value of	a reserv	•	
	4		SSI	0	R	0	1		) Presen		u 4 OC!		<b>.</b>			
								vvhe	en set, in	aicates	tnat SSI	module (	ıs pres	ent.		
	3:1		reserv	red	R	0	0	com	patibility	with fut	ure produ	ne value ucts, the lify-write	value of	a reserv		

Bit/Field	Name	Туре	Reset	Description
0	UART0	RO	1	UART0 Present
				When set, indicates that UART module 0 is present.

## Register 16: Device Capabilities 3 (DC3), offset 0x018

This register provides a list of features available in the system. The Stellaris family uses this register format to indicate the availability of the following family features in the specific device: Analog Comparator I/Os, CCP I/Os, ADC I/Os, and PWM I/Os.

Device Capabilities 3 (DC3)

Base 0x400F.E000 Offset 0x018 Type RO, reset 0x8F03.0FC0

	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16
	32KHZ		reserved		CCP3	CCP2	CCP1	CCP0			rese	rved			ADC1	ADC0
Туре	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO
Reset	1	0	0	0	1	1	1	1	0	0	0	0	0	0	1	1
	15	14	13	12	11	10	9	8	7	6	5	4	3	2	1	0
		rese	erved		C10	C1PLUS	C1MINUS	C0O	C0PLUS	C0MINUS			rese	rved	1	
Туре	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO
Reset	0	0	0	0	1	1	1	1	1	1	0	0	0	0	0	0

			•	
Bit/Field	Name	Туре	Reset	Description
31	32KHZ	RO	1	32KHz Input Clock Available
				When set, indicates an even CCP pin is present and can be used as a 32-KHz input clock.
30:28	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
27	CCP3	RO	1	CCP3 Pin Present
				When set, indicates that Capture/Compare/PWM pin 3 is present.
26	CCP2	RO	1	CCP2 Pin Present
				When set, indicates that Capture/Compare/PWM pin 2 is present.
25	CCP1	RO	1	CCP1 Pin Present
				When set, indicates that Capture/Compare/PWM pin 1 is present.
24	CCP0	RO	1	CCP0 Pin Present
				When set, indicates that Capture/Compare/PWM pin 0 is present.
23:18	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
17	ADC1	RO	1	ADC1 Pin Present
				When set, indicates that ADC pin 1 is present.
16	ADC0	RO	1	ADC0 Pin Present
				When set, indicates that ADC pin 0 is present.
15:12	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
11	C10	RO	1	C1o Pin Present
				When set, indicates that the analog comparator 1 output pin is present.

Bit/Field	Name	Туре	Reset	Description
10	C1PLUS	RO	1	C1+ Pin Present When set, indicates that the analog comparator 1 (+) input pin is present.
9	C1MINUS	RO	1	C1- Pin Present When set, indicates that the analog comparator 1 (-) input pin is present.
8	COO	RO	1	C0o Pin Present When set, indicates that the analog comparator 0 output pin is present.
7	C0PLUS	RO	1	C0+ Pin Present When set, indicates that the analog comparator 0 (+) input pin is present.
6	COMINUS	RO	1	C0- Pin Present When set, indicates that the analog comparator 0 (-) input pin is present.
5:0	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.


#### Register 17: Device Capabilities 4 (DC4), offset 0x01C

This register provides a list of features available in the system. The Stellaris family uses this register format to indicate the availability of the following family features in the specific device: Ethernet MAC and PHY, GPIOs, and CCP I/Os. The format of this register is consistent with the **RCGC2**, **SCGC2**, and **DCGC2** clock control registers and the **SRCR2** software reset control register.

Device Capabilities 4 (DC4)

Base 0x400F.E000 Offset 0x01C

Offset 0x01C Type RO, reset 0x5000.007F



Bit/Field	Name	Туре	Reset	Description
31	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
30	EPHY0	RO	1	Ethernet PHY0 Present When set, indicates that Ethernet PHY module 0 is present.
29	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
28	EMAC0	RO	1	Ethernet MAC0 Present When set, indicates that Ethernet MAC module 0 is present.
27:7	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
6	GPIOG	RO	1	GPIO Port G Present When set, indicates that GPIO Port G is present.
5	GPIOF	RO	1	GPIO Port F Present When set, indicates that GPIO Port F is present.
4	GPIOE	RO	1	GPIO Port E Present When set, indicates that GPIO Port E is present.
3	GPIOD	RO	1	GPIO Port D Present When set, indicates that GPIO Port D is present.
2	GPIOC	RO	1	GPIO Port C Present When set, indicates that GPIO Port C is present.
1	GPIOB	RO	1	GPIO Port B Present When set, indicates that GPIO Port B is present.

Bit/Field	Name	Туре	Reset	Description
0	GPIOA	RO	1	GPIO Port A Present
				When set, indicates that GPIO Port A is present.

November 18, 2011 203


## Register 18: Run Mode Clock Gating Control Register 0 (RCGC0), offset 0x100

This register controls the clock gating logic. Each bit controls a clock enable for a given interface, function, or unit. If set, the unit receives a clock and functions. Otherwise, the unit is unclocked and disabled (saving power). If the unit is unclocked, reads or writes to the unit will generate a bus fault. The reset state of these bits is 0 (unclocked) unless otherwise noted, so that all functional units are disabled. It is the responsibility of software to enable the ports necessary for the application. Note that these registers may contain more bits than there are interfaces, functions, or units to control. This is to assure reasonable code compatibility with other family and future parts. **RCGC0** is the clock configuration register for running operation, **SCGC0** for Sleep operation, and **DCGC0** for Deep-Sleep operation. Setting the ACG bit in the **Run-Mode Clock Configuration (RCC)** register specifies that the system uses sleep modes.

Run Mode Clock Gating Control Register 0 (RCGC0)

Base 0x400F.E000 Offset 0x100

Type R/W, reset 0x00000040



Bit/Field	Name	Туре	Reset	Description
31:17	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
16	ADC	R/W	0	ADC0 Clock Gating Control
				This bit controls the clock gating for SAR ADC module 0. If set, the unit receives a clock and functions. Otherwise, the unit is unclocked and disabled. If the unit is unclocked, a read or write to the unit generates a bus fault.
15:10	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
9:8	MAXADCSPD	R/W	0	ADC Sample Speed
				This field sets the rate at which the ADC samples data. You cannot set the rate higher than the maximum rate. You can set the sample rate by setting the MAXADCSPD bit as follows:
				Value Description
				0x1 250K samples/second
				0x0 125K samples/second
7	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.

Bit/Field	Name	Туре	Reset	Description
6	reserved	RO	1	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
5:4	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
3	WDT	R/W	0	WDT Clock Gating Control
				This bit controls the clock gating for the WDT module. If set, the unit receives a clock and functions. Otherwise, the unit is unclocked and disabled. If the unit is unclocked, a read or write to the unit generates a bus fault.
2:0	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.

# Register 19: Sleep Mode Clock Gating Control Register 0 (SCGC0), offset 0x110

This register controls the clock gating logic. Each bit controls a clock enable for a given interface, function, or unit. If set, the unit receives a clock and functions. Otherwise, the unit is unclocked and disabled (saving power). If the unit is unclocked, reads or writes to the unit will generate a bus fault. The reset state of these bits is 0 (unclocked) unless otherwise noted, so that all functional units are disabled. It is the responsibility of software to enable the ports necessary for the application. Note that these registers may contain more bits than there are interfaces, functions, or units to control. This is to assure reasonable code compatibility with other family and future parts. **RCGC0** is the clock configuration register for running operation, **SCGC0** for Sleep operation, and **DCGC0** for Deep-Sleep operation. Setting the ACG bit in the **Run-Mode Clock Configuration (RCC)** register specifies that the system uses sleep modes.

Sleep Mode Clock Gating Control Register 0 (SCGC0)

Base 0x400F.E000 Offset 0x110 Type R/W, reset 0x00000040

_	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16
		)	1	1		1	1	reserved	1			1	1	1	_	ADC
Type •	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	R/W
Reset	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0
_	15	14	13	12	11	10	9	8	7	6	5	4	3	2	1	0
			rese	rved	!	'	MAXA	DCSPD	reserved	reserved	rese	rved	WDT		reserved	
Туре	RO	RO	RO	RO	RO	RO	R/W	R/W	RO	RO	RO	RO	R/W	RO	RO	RO
Reset	0	0	0	0	0	0	0	0	0	1	0	0	0	0	0	0

D:#/Field	Nama	T	Danet	Description
Bit/Field	Name	Type	Reset	Description
31:17	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
16	ADC	R/W	0	ADC0 Clock Gating Control
				This bit controls the clock gating for SAR ADC module 0. If set, the unit receives a clock and functions. Otherwise, the unit is unclocked and disabled. If the unit is unclocked, a read or write to the unit generates a bus fault.
15:10	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
9:8	MAXADCSPD	R/W	0	ADC Sample Speed
				This field sets the rate at which the ADC samples data. You cannot set the rate higher than the maximum rate. You can set the sample rate by setting the MAXADCSPD bit as follows:
				Value Description
				0x1 250K samples/second
				0x0 125K samples/second
7	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.

Bit/Field	Name	Туре	Reset	Description
6	reserved	RO	1	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
5:4	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
3	WDT	R/W	0	WDT Clock Gating Control
				This bit controls the clock gating for the WDT module. If set, the unit receives a clock and functions. Otherwise, the unit is unclocked and disabled. If the unit is unclocked, a read or write to the unit generates a bus fault.
2:0	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.

# Register 20: Deep Sleep Mode Clock Gating Control Register 0 (DCGC0), offset 0x120

This register controls the clock gating logic. Each bit controls a clock enable for a given interface, function, or unit. If set, the unit receives a clock and functions. Otherwise, the unit is unclocked and disabled (saving power). If the unit is unclocked, reads or writes to the unit will generate a bus fault. The reset state of these bits is 0 (unclocked) unless otherwise noted, so that all functional units are disabled. It is the responsibility of software to enable the ports necessary for the application. Note that these registers may contain more bits than there are interfaces, functions, or units to control. This is to assure reasonable code compatibility with other family and future parts. **RCGC0** is the clock configuration register for running operation, **SCGC0** for Sleep operation, and **DCGC0** for Deep-Sleep operation. Setting the ACG bit in the **Run-Mode Clock Configuration (RCC)** register specifies that the system uses sleep modes.

Deep Sleep Mode Clock Gating Control Register 0 (DCGC0)

Base 0x400F.E000 Offset 0x120

Type R/W, reset 0x00000040

	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16
			'	1			•	reserved	1	'			1	1		ADC
Туре	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	R/W
Reset	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0
	15	14	13	12	11	10	9	8	7	6	5	4	3	2	1	0
			•	1	reserved		•	'		reserved	rese	rved	WDT		reserved	'
Туре	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	R/W	RO	RO	RO
Reset	0	0	0	0	0	0	0	0	0	1	0	0	0	0	0	0
В	Bit/Field		Nan	ne	Ту	ре	Reset	Des	cription							
	31:17		reser	ved	R	0	0				-				t. To prov ved bit sh	

Bit/Field	Name	Туре	Reset	Description
31:17	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
16	ADC	R/W	0	ADC0 Clock Gating Control
				This bit controls the clock gating for SAR ADC module 0. If set, the unit receives a clock and functions. Otherwise, the unit is unclocked and disabled. If the unit is unclocked, a read or write to the unit generates a bus fault.
15:7	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
6	reserved	RO	1	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
5:4	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
3	WDT	R/W	0	WDT Clock Gating Control
				This bit controls the clock gating for the WDT module. If set, the unit receives a clock and functions. Otherwise, the unit is unclocked and disabled. If the unit is unclocked, a read or write to the unit generates

a bus fault.

Bit/Field	Name	Type	Reset	Description
2:0	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.

#### Register 21: Run Mode Clock Gating Control Register 1 (RCGC1), offset 0x104

This register controls the clock gating logic. Each bit controls a clock enable for a given interface, function, or unit. If set, the unit receives a clock and functions. Otherwise, the unit is unclocked and disabled (saving power). If the unit is unclocked, reads or writes to the unit will generate a bus fault. The reset state of these bits is 0 (unclocked) unless otherwise noted, so that all functional units are disabled. It is the responsibility of software to enable the ports necessary for the application. Note that these registers may contain more bits than there are interfaces, functions, or units to control. This is to assure reasonable code compatibility with other family and future parts. RCGC1 is the clock configuration register for running operation, SCGC1 for Sleep operation, and DCGC1 for Deep-Sleep operation. Setting the ACG bit in the Run-Mode Clock Configuration (RCC) register specifies that the system uses sleep modes.

23

21

20

19

17

Run Mode Clock Gating Control Register 1 (RCGC1)

COMP0

reserved

TIMER2

R/W

RO

R/W

0

0

28

26

25

Base 0x400F.E000 Offset 0x104

31


24

23:19

18

Type R/W, reset 0x00000000

30



24

0 Analog Comparator 0 Clock Gating

This bit controls the clock gating for analog comparator 0. If set, the unit receives a clock and functions. Otherwise, the unit is unclocked and disabled. If the unit is unclocked, reads or writes to the unit will generate a bus fault.

Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.

Timer 2 Clock Gating Control

This bit controls the clock gating for General-Purpose Timer module 2. If set, the unit receives a clock and functions. Otherwise, the unit is unclocked and disabled. If the unit is unclocked, reads or writes to the unit will generate a bus fault.

Bit/Field	Name	Туре	Reset	Description
17	TIMER1	R/W	0	Timer 1 Clock Gating Control
				This bit controls the clock gating for General-Purpose Timer module 1. If set, the unit receives a clock and functions. Otherwise, the unit is unclocked and disabled. If the unit is unclocked, reads or writes to the unit will generate a bus fault.
16	TIMER0	R/W	0	Timer 0 Clock Gating Control
				This bit controls the clock gating for General-Purpose Timer module 0. If set, the unit receives a clock and functions. Otherwise, the unit is unclocked and disabled. If the unit is unclocked, reads or writes to the unit will generate a bus fault.
15:5	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
4	SSI0	R/W	0	SSI0 Clock Gating Control
				This bit controls the clock gating for SSI module 0. If set, the unit receives a clock and functions. Otherwise, the unit is unclocked and disabled. If the unit is unclocked, reads or writes to the unit will generate a bus fault.
3:1	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
0	UART0	R/W	0	UART0 Clock Gating Control
				This bit controls the clock gating for UART module 0. If set, the unit receives a clock and functions. Otherwise, the unit is unclocked and disabled. If the unit is unclocked, reads or writes to the unit will generate a bus fault.

# Register 22: Sleep Mode Clock Gating Control Register 1 (SCGC1), offset 0x114

This register controls the clock gating logic. Each bit controls a clock enable for a given interface, function, or unit. If set, the unit receives a clock and functions. Otherwise, the unit is unclocked and disabled (saving power). If the unit is unclocked, reads or writes to the unit will generate a bus fault. The reset state of these bits is 0 (unclocked) unless otherwise noted, so that all functional units are disabled. It is the responsibility of software to enable the ports necessary for the application. Note that these registers may contain more bits than there are interfaces, functions, or units to control. This is to assure reasonable code compatibility with other family and future parts. **RCGC1** is the clock configuration register for running operation, **SCGC1** for Sleep operation, and **DCGC1** for Deep-Sleep operation. Setting the ACG bit in the **Run-Mode Clock Configuration (RCC)** register specifies that the system uses sleep modes.

Sleep Mode Clock Gating Control Register 1 (SCGC1)

Base 0x400F.E000 Offset 0x114 Type R/W, reset 0x00000000

	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16
		1	rese	rved	1	1	COMP1	COMP0			reserved			TIMER2	TIMER1	TIMER0
Туре	RO	RO	RO	RO	RO	RO	R/W	R/W	RO	RO	RO	RO	RO	R/W	R/W	R/W
Reset	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0
	15	14	13	12	11	10	9	8	7	6	5	4	3	2	1	0
		1				reserved						SSI0		reserved		UART0
Туре	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	R/W	RO	RO	RO	R/W
Reset	Λ	Λ	Λ	Λ	Λ	Λ	Λ	Λ	Λ	Λ	Λ	Λ	Λ	Λ	Λ	Λ

Bit/Field	Name	Туре	Reset	Description
31:26	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
25	COMP1	R/W	0	Analog Comparator 1 Clock Gating
				This bit controls the clock gating for analog comparator 1. If set, the unit receives a clock and functions. Otherwise, the unit is unclocked and disabled. If the unit is unclocked, reads or writes to the unit will generate a bus fault.
24	COMP0	R/W	0	Analog Comparator 0 Clock Gating
				This bit controls the clock gating for analog comparator 0. If set, the unit receives a clock and functions. Otherwise, the unit is unclocked and disabled. If the unit is unclocked, reads or writes to the unit will generate a bus fault.
23:19	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
18	TIMER2	R/W	0	Timer 2 Clock Gating Control
				This bit controls the clock gating for General-Purpose Timer module 2. If set, the unit receives a clock and functions. Otherwise, the unit is unclocked and disabled. If the unit is unclocked, reads or writes to the

unit will generate a bus fault.

Bit/Field	Name	Туре	Reset	Description
17	TIMER1	R/W	0	Timer 1 Clock Gating Control  This bit controls the clock gating for General-Purpose Timer module 1.  If set, the unit receives a clock and functions. Otherwise, the unit is unclocked and disabled. If the unit is unclocked, reads or writes to the unit will generate a bus fault.
16	TIMER0	R/W	0	Timer 0 Clock Gating Control  This bit controls the clock gating for General-Purpose Timer module 0.  If set, the unit receives a clock and functions. Otherwise, the unit is unclocked and disabled. If the unit is unclocked, reads or writes to the unit will generate a bus fault.
15:5	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
4	SSI0	R/W	0	SSI0 Clock Gating Control  This bit controls the clock gating for SSI module 0. If set, the unit receives a clock and functions. Otherwise, the unit is unclocked and disabled. If the unit is unclocked, reads or writes to the unit will generate a bus fault.
3:1	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
0	UART0	R/W	0	UART0 Clock Gating Control  This bit controls the clock gating for UART module 0. If set, the unit receives a clock and functions. Otherwise, the unit is unclocked and disabled. If the unit is unclocked, reads or writes to the unit will generate a bus fault.

# Register 23: Deep Sleep Mode Clock Gating Control Register 1 (DCGC1), offset 0x124

This register controls the clock gating logic. Each bit controls a clock enable for a given interface, function, or unit. If set, the unit receives a clock and functions. Otherwise, the unit is unclocked and disabled (saving power). If the unit is unclocked, reads or writes to the unit will generate a bus fault. The reset state of these bits is 0 (unclocked) unless otherwise noted, so that all functional units are disabled. It is the responsibility of software to enable the ports necessary for the application. Note that these registers may contain more bits than there are interfaces, functions, or units to control. This is to assure reasonable code compatibility with other family and future parts. **RCGC1** is the clock configuration register for running operation, **SCGC1** for Sleep operation, and **DCGC1** for Deep-Sleep operation. Setting the ACG bit in the **Run-Mode Clock Configuration (RCC)** register specifies that the system uses sleep modes.

Deep Sleep Mode Clock Gating Control Register 1 (DCGC1)

Base 0x400F.E000 Offset 0x124

Type R/W, reset 0x00000000

_	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16
	'		rese	rved			COMP1	COMP0		'	reserved			TIMER2	TIMER1	TIMER0
Type Reset	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	R/W 0	R/W 0	RO 0	RO 0	RO 0	RO 0	RO 0	R/W 0	R/W 0	R/W 0
_	15	14	13	12	11	10	9	8	7	6	5	4	3	2	1	0
	'		1			reserved				'		SSI0		reserved	l	UART0
Type Reset	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	R/W 0	RO 0	RO 0	RO 0	R/W 0
В	Bit/Field		Nam	ne	Ту	ре	Reset	Des	cription							
	31:26		reserv	ved	R	0	0	com	patibility		ıre produ	icts, the	value of	erved bit a reserv on.	•	
	25		COMP1		R/W		0	Ana	Analog Comparator 1 Clock Gating							
								rece disa	ives a c	lock and	function	s. Other	wise, the	mparator e unit is u es to the u	ınclocke	d and
	24		COMP0		R/W		0	Ana	Analog Comparator 0 Clock Gating							
								rece disa	This bit controls the clock gating for analog comparator 0. If set, the unit receives a clock and functions. Otherwise, the unit is unclocked and disabled. If the unit is unclocked, reads or writes to the unit will generate a bus fault.							
	23:19		reserv	ved	RO		0	com	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should preserved across a read-modify-write operation.							
	18		TIME	R2	R/	W	0	Time	er 2 Cloc	ck Gating	Control					
								If se uncl	t, the un ocked a	it receive	es a cloc led. If the	k and fur	nctions.	Purpose Otherwised, reads	e, the u	nit is

Bit/Field	Name	Туре	Reset	Description
17	TIMER1	R/W	0	Timer 1 Clock Gating Control  This bit controls the clock gating for Coneral Purpose Timer module 1
				This bit controls the clock gating for General-Purpose Timer module 1. If set, the unit receives a clock and functions. Otherwise, the unit is unclocked and disabled. If the unit is unclocked, reads or writes to the unit will generate a bus fault.
16	TIMER0	R/W	0	Timer 0 Clock Gating Control
				This bit controls the clock gating for General-Purpose Timer module 0. If set, the unit receives a clock and functions. Otherwise, the unit is unclocked and disabled. If the unit is unclocked, reads or writes to the unit will generate a bus fault.
15:5	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
4	SSI0	R/W	0	SSI0 Clock Gating Control
				This bit controls the clock gating for SSI module 0. If set, the unit receives a clock and functions. Otherwise, the unit is unclocked and disabled. If the unit is unclocked, reads or writes to the unit will generate a bus fault.
3:1	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
0	UART0	R/W	0	UART0 Clock Gating Control
				This bit controls the clock gating for UART module 0. If set, the unit receives a clock and functions. Otherwise, the unit is unclocked and disabled. If the unit is unclocked, reads or writes to the unit will generate a bus fault.


## Register 24: Run Mode Clock Gating Control Register 2 (RCGC2), offset 0x108

This register controls the clock gating logic. Each bit controls a clock enable for a given interface, function, or unit. If set, the unit receives a clock and functions. Otherwise, the unit is unclocked and disabled (saving power). If the unit is unclocked, reads or writes to the unit will generate a bus fault. The reset state of these bits is 0 (unclocked) unless otherwise noted, so that all functional units are disabled. It is the responsibility of software to enable the ports necessary for the application. Note that these registers may contain more bits than there are interfaces, functions, or units to control. This is to assure reasonable code compatibility with other family and future parts. RCGC2 is the clock configuration register for running operation, SCGC2 for Sleep operation, and DCGC2 for Deep-Sleep operation. Setting the ACG bit in the Run-Mode Clock Configuration (RCC) register specifies that the system uses sleep modes.

Run Mode Clock Gating Control Register 2 (RCGC2)

Base 0x400F.E000 Offset 0x108

Type R/W, reset 0x00000000



Bit/Field	Name	Type	Reset	Description
31	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
30	EPHY0	R/W	0	PHY0 Clock Gating Control
				This bit controls the clock gating for Ethernet PHY unit 0. If set, the unit receives a clock and functions. Otherwise, the unit is unclocked and disabled. If the unit is unclocked, reads or writes to the unit will generate a bus fault.
29	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
28	EMAC0	R/W	0	MAC0 Clock Gating Control
				This bit controls the clock gating for Ethernet MAC unit 0. If set, the unit receives a clock and functions. Otherwise, the unit is unclocked and disabled. If the unit is unclocked, reads or writes to the unit will generate a bus fault.
27:7	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
6	GPIOG	R/W	0	Port G Clock Gating Control
				This bit controls the clock gating for Port G. If set, the unit receives a clock and functions. Otherwise, the unit is unclocked and disabled. If

the unit is unclocked, reads or writes to the unit will generate a bus fault.

Bit/Field	Name	Туре	Reset	Description
5	GPIOF	R/W	0	Port F Clock Gating Control  This bit controls the clock gating for Port F. If set, the unit receives a clock and functions. Otherwise, the unit is unclocked and disabled. If the unit is unclocked, reads or writes to the unit will generate a bus fault.
4	GPIOE	R/W	0	Port E Clock Gating Control  This bit controls the clock gating for Port E. If set, the unit receives a clock and functions. Otherwise, the unit is unclocked and disabled. If the unit is unclocked, reads or writes to the unit will generate a bus fault.
3	GPIOD	R/W	0	Port D Clock Gating Control  This bit controls the clock gating for Port D. If set, the unit receives a clock and functions. Otherwise, the unit is unclocked and disabled. If the unit is unclocked, reads or writes to the unit will generate a bus fault.
2	GPIOC	R/W	0	Port C Clock Gating Control  This bit controls the clock gating for Port C. If set, the unit receives a clock and functions. Otherwise, the unit is unclocked and disabled. If the unit is unclocked, reads or writes to the unit will generate a bus fault.
1	GPIOB	R/W	0	Port B Clock Gating Control  This bit controls the clock gating for Port B. If set, the unit receives a clock and functions. Otherwise, the unit is unclocked and disabled. If the unit is unclocked, reads or writes to the unit will generate a bus fault.
0	GPIOA	R/W	0	Port A Clock Gating Control  This bit controls the clock gating for Port A. If set, the unit receives a clock and functions. Otherwise, the unit is unclocked and disabled. If the unit is unclocked, reads or writes to the unit will generate a bus fault.

# Register 25: Sleep Mode Clock Gating Control Register 2 (SCGC2), offset 0x118

This register controls the clock gating logic. Each bit controls a clock enable for a given interface, function, or unit. If set, the unit receives a clock and functions. Otherwise, the unit is unclocked and disabled (saving power). If the unit is unclocked, reads or writes to the unit will generate a bus fault. The reset state of these bits is 0 (unclocked) unless otherwise noted, so that all functional units are disabled. It is the responsibility of software to enable the ports necessary for the application. Note that these registers may contain more bits than there are interfaces, functions, or units to control. This is to assure reasonable code compatibility with other family and future parts. RCGC2 is the clock configuration register for running operation, SCGC2 for Sleep operation, and DCGC2 for Deep-Sleep operation. Setting the ACG bit in the Run-Mode Clock Configuration (RCC) register specifies that the system uses sleep modes.

Sleep Mode Clock Gating Control Register 2 (SCGC2)

Base 0x400F.E000 Offset 0x118 Type R/W, reset 0x00000000

	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16
	reserved	EPHY0	reserved	EMAC0			1	1	1	rese	rved					4
Type	RO	R/W	RO	R/W	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO
Reset	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0
									_		_					
	15	14	13	12	11	10	9	8	7	6	5	4	3	2	1	0
		'	'	•	reserved		'	1	! !	GPIOG	GPIOF	GPIOE	GPIOD	GPIOC	GPIOB	GPIOA
Туре	RO	RO	RO	RO	RO	RO	RO	RO	RO	R/W						
Donot	0	0	0	^	0	0	0	0	0	0	0	^	0	0	0	0

Bit/Field	Name	Туре	Reset	Description
31	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
30	EPHY0	R/W	0	PHY0 Clock Gating Control
				This bit controls the clock gating for Ethernet PHY unit 0. If set, the unit receives a clock and functions. Otherwise, the unit is unclocked and disabled. If the unit is unclocked, reads or writes to the unit will generate a bus fault.
29	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
28	EMAC0	R/W	0	MAC0 Clock Gating Control
				This bit controls the clock gating for Ethernet MAC unit 0. If set, the unit receives a clock and functions. Otherwise, the unit is unclocked and disabled. If the unit is unclocked, reads or writes to the unit will generate a bus fault.
27:7	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
6	GPIOG	R/W	0	Port G Clock Gating Control
				This bit controls the clock gating for Port G. If set, the unit receives a clock and functions. Otherwise, the unit is unclocked and disabled. If the unit is unclocked, reads or writes to the unit will generate a bus fault.

Bit/Field	Name	Туре	Reset	Description
5	GPIOF	R/W	0	Port F Clock Gating Control  This bit controls the clock gating for Port F. If set, the unit receives a
				clock and functions. Otherwise, the unit is unclocked and disabled. If the unit is unclocked, reads or writes to the unit will generate a bus fault.
4	GPIOE	R/W	0	Port E Clock Gating Control
				This bit controls the clock gating for Port E. If set, the unit receives a clock and functions. Otherwise, the unit is unclocked and disabled. If the unit is unclocked, reads or writes to the unit will generate a bus fault.
3	GPIOD	R/W	0	Port D Clock Gating Control
				This bit controls the clock gating for Port D. If set, the unit receives a clock and functions. Otherwise, the unit is unclocked and disabled. If the unit is unclocked, reads or writes to the unit will generate a bus fault.
2	GPIOC	R/W	0	Port C Clock Gating Control
				This bit controls the clock gating for Port C. If set, the unit receives a clock and functions. Otherwise, the unit is unclocked and disabled. If the unit is unclocked, reads or writes to the unit will generate a bus fault.
1	GPIOB	R/W	0	Port B Clock Gating Control
				This bit controls the clock gating for Port B. If set, the unit receives a clock and functions. Otherwise, the unit is unclocked and disabled. If the unit is unclocked, reads or writes to the unit will generate a bus fault.
0	GPIOA	R/W	0	Port A Clock Gating Control
				This bit controls the clock gating for Port A. If set, the unit receives a clock and functions. Otherwise, the unit is unclocked and disabled. If the unit is unclocked, reads or writes to the unit will generate a bus fault.

# Register 26: Deep Sleep Mode Clock Gating Control Register 2 (DCGC2), offset 0x128

This register controls the clock gating logic. Each bit controls a clock enable for a given interface, function, or unit. If set, the unit receives a clock and functions. Otherwise, the unit is unclocked and disabled (saving power). If the unit is unclocked, reads or writes to the unit will generate a bus fault. The reset state of these bits is 0 (unclocked) unless otherwise noted, so that all functional units are disabled. It is the responsibility of software to enable the ports necessary for the application. Note that these registers may contain more bits than there are interfaces, functions, or units to control. This is to assure reasonable code compatibility with other family and future parts. RCGC2 is the clock configuration register for running operation, SCGC2 for Sleep operation, and DCGC2 for Deep-Sleep operation. Setting the ACG bit in the Run-Mode Clock Configuration (RCC) register specifies that the system uses sleep modes.

Deep Sleep Mode Clock Gating Control Register 2 (DCGC2)

Base 0x400F.E000 Offset 0x128 Type R/W, reset 0x00000000

	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16
	reserved	EPHY0	reserved	EMAC0			1	1	1	rese	rved					4
Type	RO	R/W	RO	R/W	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO
Reset	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0
									_		_					
	15	14	13	12	11	10	9	8	7	6	5	4	3	2	1	0
		'	'	•	reserved		'	1	! !	GPIOG	GPIOF	GPIOE	GPIOD	GPIOC	GPIOB	GPIOA
Туре	RO	RO	RO	RO	RO	RO	RO	RO	RO	R/W						
Donot	0	0	0	^	0	0	0	0	0	0	0	^	0	0	0	0

Bit/Field	Name	Туре	Reset	Description
31	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
30	EPHY0	R/W	0	PHY0 Clock Gating Control
				This bit controls the clock gating for Ethernet PHY unit 0. If set, the unit receives a clock and functions. Otherwise, the unit is unclocked and disabled. If the unit is unclocked, reads or writes to the unit will generate a bus fault.
29	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
28	EMAC0	R/W	0	MAC0 Clock Gating Control
				This bit controls the clock gating for Ethernet MAC unit 0. If set, the unit receives a clock and functions. Otherwise, the unit is unclocked and disabled. If the unit is unclocked, reads or writes to the unit will generate a bus fault.
27:7	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
6	GPIOG	R/W	0	Port G Clock Gating Control
				This bit controls the clock gating for Port G. If set, the unit receives a clock and functions. Otherwise, the unit is unclocked and disabled. If the unit is unclocked, reads or writes to the unit will generate a bus fault.

Bit/Field	Name	Туре	Reset	Description
5	GPIOF	R/W	0	Port F Clock Gating Control  This bit controls the clock gating for Port F. If set, the unit receives a
				clock and functions. Otherwise, the unit is unclocked and disabled. If the unit is unclocked, reads or writes to the unit will generate a bus fault.
4	GPIOE	R/W	0	Port E Clock Gating Control
				This bit controls the clock gating for Port E. If set, the unit receives a clock and functions. Otherwise, the unit is unclocked and disabled. If the unit is unclocked, reads or writes to the unit will generate a bus fault.
3	GPIOD	R/W	0	Port D Clock Gating Control
				This bit controls the clock gating for Port D. If set, the unit receives a clock and functions. Otherwise, the unit is unclocked and disabled. If the unit is unclocked, reads or writes to the unit will generate a bus fault.
2	GPIOC	R/W	0	Port C Clock Gating Control
				This bit controls the clock gating for Port C. If set, the unit receives a clock and functions. Otherwise, the unit is unclocked and disabled. If the unit is unclocked, reads or writes to the unit will generate a bus fault.
1	GPIOB	R/W	0	Port B Clock Gating Control
				This bit controls the clock gating for Port B. If set, the unit receives a clock and functions. Otherwise, the unit is unclocked and disabled. If the unit is unclocked, reads or writes to the unit will generate a bus fault.
0	GPIOA	R/W	0	Port A Clock Gating Control
				This bit controls the clock gating for Port A. If set, the unit receives a clock and functions. Otherwise, the unit is unclocked and disabled. If the unit is unclocked, reads or writes to the unit will generate a bus fault.

November 18, 2011 221


# Register 27: Software Reset Control 0 (SRCR0), offset 0x040

Writes to this register are masked by the bits in the **Device Capabilities 1 (DC1)** register.

#### Software Reset Control 0 (SRCR0)

Base 0x400F.E000

Offset 0x040 Type R/W, reset 0x00000000



Bit/Field	Name	Type	Reset	Description
31:17	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
16	ADC	R/W	0	ADC0 Reset Control
				Reset control for SAR ADC module 0.
15:4	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
3	WDT	R/W	0	WDT Reset Control
				Reset control for Watchdog unit.
2:0	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.


## Register 28: Software Reset Control 1 (SRCR1), offset 0x044

Writes to this register are masked by the bits in the Device Capabilities 2 (DC2) register.

#### Software Reset Control 1 (SRCR1)

Base 0x400F.E000 Offset 0x044

Type R/W, reset 0x00000000



	,	0 0	Ü	
Bit/Field	Name	Туре	Reset	Description
31:26	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
25	COMP1	R/W	0	Analog Comp 1 Reset Control Reset control for analog comparator 1.
24	COMP0	R/W	0	Analog Comp 0 Reset Control Reset control for analog comparator 0.
23:19	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
18	TIMER2	R/W	0	Timer 2 Reset Control Reset control for General-Purpose Timer module 2.
17	TIMER1	R/W	0	Timer 1 Reset Control  Reset control for General-Purpose Timer module 1.
16	TIMER0	R/W	0	Timer 0 Reset Control Reset control for General-Purpose Timer module 0.
15:5	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
4	SSI0	R/W	0	SSI0 Reset Control Reset control for SSI unit 0.
3:1	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
0	UART0	R/W	0	UART0 Reset Control Reset control for UART unit 0.

## Register 29: Software Reset Control 2 (SRCR2), offset 0x048

Writes to this register are masked by the bits in the **Device Capabilities 4 (DC4)** register.

#### Software Reset Control 2 (SRCR2)

Base 0x400F.E000

Offset 0x048
Type R/W, reset 0x00000000

	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16
	reserved	EPHY0	reserved	EMAC0			1	1	1	rese	rved					
Type	RO	R/W	RO	R/W	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO
Reset	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0
	15	14	13	12	11	10	9	8	7	6	5	4	3	2	1	0
		1	1		reserved					GPIOG	GPIOF	GPIOE	GPIOD	GPIOC	GPIOB	GPIOA
Туре	RO	RO	RO	RO	RO	RO	RO	RO	RO	R/W						
Docot	Λ	Λ	Λ	Λ	Λ	Λ	Λ	Λ	Λ	Λ	Λ	Λ	Λ	Λ	Λ	Λ

Bit/Field	Name	Туре	Reset	Description
31	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
30	EPHY0	R/W	0	PHY0 Reset Control Reset control for Ethernet PHY unit 0.
29	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
28	EMAC0	R/W	0	MAC0 Reset Control
				Reset control for Ethernet MAC unit 0.
27:7	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
6	GPIOG	R/W	0	Port G Reset Control Reset control for GPIO Port G.
5	GPIOF	R/W	0	Port F Reset Control Reset control for GPIO Port F.
4	GPIOE	R/W	0	Port E Reset Control Reset control for GPIO Port E.
3	GPIOD	R/W	0	Port D Reset Control Reset control for GPIO Port D.
2	GPIOC	R/W	0	Port C Reset Control Reset control for GPIO Port C.
1	GPIOB	R/W	0	Port B Reset Control Reset control for GPIO Port B.
0	GPIOA	R/W	0	Port A Reset Control Reset control for GPIO Port A.


# 6 Internal Memory

The LM3S6422 microcontroller comes with 32 KB of bit-banded SRAM and 96 KB of flash memory. The flash controller provides a user-friendly interface, making flash programming a simple task. Flash protection can be applied to the flash memory on a 2-KB block basis.

## 6.1 Block Diagram

Figure 6-1 on page 225 illustrates the Flash functions. The dashed boxes in the figure indicate registers residing in the System Control module rather than the Flash Control module.

Figure 6-1. Flash Block Diagram



# 6.2 Functional Description

This section describes the functionality of the SRAM and Flash memories.

### 6.2.1 SRAM Memory

The internal SRAM of the Stellaris<sup>®</sup> devices is located at address 0x2000.0000 of the device memory map. To reduce the number of time consuming read-modify-write (RMW) operations, ARM has introduced *bit-banding* technology in the Cortex-M3 processor. With a bit-band-enabled processor, certain regions in the memory map (SRAM and peripheral space) can use address aliases to access individual bits in a single, atomic operation.

The bit-band alias is calculated by using the formula:

```
bit-band alias = bit-band base + (byte offset * 32) + (bit number * 4)
```

For example, if bit 3 at address 0x2000.1000 is to be modified, the bit-band alias is calculated as:

```
0x2200.0000 + (0x1000 * 32) + (3 * 4) = 0x2202.000C
```

With the alias address calculated, an instruction performing a read/write to address 0x2202.000C allows direct access to only bit 3 of the byte at address 0x2000.1000.

For details about bit-banding, see "Bit-Banding" on page 67.

### 6.2.2 Flash Memory

The flash is organized as a set of 1-KB blocks that can be individually erased. Erasing a block causes the entire contents of the block to be reset to all 1s. An individual 32-bit word can be programmed to change bits that are currently 1 to a 0. These blocks are paired into a set of 2-KB blocks that can be individually protected. The protection allows blocks to be marked as read-only or execute-only, providing different levels of code protection. Read-only blocks cannot be erased or programmed, protecting the contents of those blocks from being modified. Execute-only blocks cannot be erased or programmed, and can only be read by the controller instruction fetch mechanism, protecting the contents of those blocks from being read by either the controller or by a debugger.

See also "Serial Flash Loader" on page 575 for a preprogrammed flash-resident utility used to download code to the flash memory of a device without the use of a debug interface.

### 6.2.2.1 Flash Memory Timing

The timing for the flash is automatically handled by the flash controller. However, in order to do so, it must know the clock rate of the system in order to time its internal signals properly. The number of clock cycles per microsecond must be provided to the flash controller for it to accomplish this timing. It is software's responsibility to keep the flash controller updated with this information via the **USec Reload (USECRL)** register.

On reset, the **USECRL** register is loaded with a value that configures the flash timing so that it works with the maximum clock rate of the part. If software changes the system operating frequency, the new operating frequency minus 1 (in MHz) must be loaded into **USECRL** before any flash modifications are attempted. For example, if the device is operating at a speed of 20 MHz, a value of 0x13 (20-1) must be written to the **USECRL** register.

#### 6.2.2.2 Flash Memory Protection

The user is provided two forms of flash protection per 2-KB flash blocks in two pairs of 32-bit wide registers. The protection policy for each form is controlled by individual bits (per policy per block) in the **FMPPEn** and **FMPREn** registers.

- Flash Memory Protection Program Enable (FMPPEn): If set, the block may be programmed (written) or erased. If cleared, the block may not be changed.
- Flash Memory Protection Read Enable (FMPREn): If a bit is set, the corresponding block may be executed or read by software or debuggers. If a bit is cleared, the corresponding block may only be executed, and contents of the memory block are prohibited from being read as data.

The policies may be combined as shown in Table 6-1 on page 226.

**Table 6-1. Flash Protection Policy Combinations** 

FMPPEn	FMPREn	Protection
0	0	Execute-only protection. The block may only be executed and may not be written or erased.
		This mode is used to protect code.

Table 6-1. Flash Protection Policy Combinations (continued)

FMPPEn	FMPREn	Protection
1	0	The block may be written, erased or executed, but not read. This combination is unlikely to be used.
0	1	Read-only protection. The block may be read or executed but may not be written or erased. This mode is used to lock the block from further modification while allowing any read or execute access.
1	1	No protection. The block may be written, erased, executed or read.

A Flash memory access that attempts to read a read-protected block (**FMPREn** bit is set) is prohibited and generates a bus fault. A Flash memory access that attempts to program or erase a program-protected block (**FMPPEn** bit is set) is prohibited and can optionally generate an interrupt (by setting the AMASK bit in the **Flash Controller Interrupt Mask (FCIM)** register) to alert software developers of poorly behaving software during the development and debug phases.

The factory settings for the **FMPREn** and **FMPPEn** registers are a value of 1 for all implemented banks. These settings create a policy of open access and programmability. The register bits may be changed by clearing the specific register bit. The changes are not permanent until the register is committed (saved), at which point the bit change is permanent. If a bit is changed from a 1 to a 0 and not committed, it may be restored by executing a power-on reset sequence. The changes are committed using the **Flash Memory Control (FMC)** register. Details on programming these bits are discussed in "Nonvolatile Register Programming" on page 228.

#### 6.2.2.3 Interrupts

The Flash memory controller can generate interrupts when the following conditions are observed:

- Programming Interrupt signals when a program or erase action is complete.
- Access Interrupt signals when a program or erase action has been attempted on a 2-kB block of memory that is protected by its corresponding FMPPEn bit.

The interrupt events that can trigger a controller-level interrupt are defined in the **Flash Controller Masked Interrupt Status (FCMIS)** register (see page 236) by setting the corresponding MASK bits. If interrupts are not used, the raw interrupt status is always visible via the **Flash Controller Raw Interrupt Status (FCRIS)** register (see page 235).

Interrupts are always cleared (for both the **FCMIS** and **FCRIS** registers) by writing a 1 to the corresponding bit in the **Flash Controller Masked Interrupt Status and Clear (FCMISC)** register (see page 237).

# 6.3 Flash Memory Initialization and Configuration

## 6.3.1 Flash Programming

The Stellaris devices provide a user-friendly interface for flash programming. All erase/program operations are handled via three registers: **FMA**, **FMD**, and **FMC**.

During a Flash memory operation (write, page erase, or mass erase) access to the Flash memory is inhibited. As a result, instruction and literal fetches are held off until the Flash memory operation is complete. If instruction execution is required during a Flash memory operation, the code that is executing must be placed in SRAM and executed from there while the flash operation is in progress.

#### 6.3.1.1 To program a 32-bit word

- Write source data to the FMD register.
- 2. Write the target address to the **FMA** register.
- 3. Write the flash write key and the WRITE bit (a value of 0xA442.0001) to the FMC register.
- 4. Poll the FMC register until the WRITE bit is cleared.

#### 6.3.1.2 To perform an erase of a 1-KB page

- 1. Write the page address to the **FMA** register.
- 2. Write the flash write key and the ERASE bit (a value of 0xA442.0002) to the FMC register.
- 3. Poll the FMC register until the ERASE bit is cleared.

#### 6.3.1.3 To perform a mass erase of the flash

- 1. Write the flash write key and the MERASE bit (a value of 0xA442.0004) to the FMC register.
- 2. Poll the FMC register until the MERASE bit is cleared.

### 6.3.2 Nonvolatile Register Programming

This section discusses how to update registers that are resident within the Flash memory itself. These registers exist in a separate space from the main Flash memory array and are not affected by an ERASE or MASS ERASE operation. The bits in these registers can be changed from 1 to 0 with a write operation. Prior to being committed, the register contents are unaffected by any reset condition except power-on reset, which returns the register contents to the original value. By committing the register values using the COMT bit in the **FMC** register, the register contents become nonvolatile and are therefore retained following power cycling. Once the register contents are committed, the contents are permanent, and they cannot be restored to their factory default values.

With the exception of the **USER\_DBG** register, the settings in these registers can be tested before committing them to Flash memory. For the **USER\_DBG** register, the data to be written is loaded into the **FMD** register before it is committed. The **FMD** register is read only and does not allow the **USER\_DBG** operation to be tried before committing it to nonvolatile memory.

**Important:** The Flash memory registers can only have bits changed from 1 to 0 by user programming and can only be committed once. After being committed, these registers cannot be restored to their factory default values.

In addition, the USER\_REG0, USER\_REG1, USER\_REG2, USER\_REG3, and USER\_DBG registers each use bit 31 (NW) to indicate that they have not been committed and bits in the register may be changed from 1 to 0. These five registers can only be committed once whereas the Flash memory protection registers may be committed multiple times. Table 6-2 on page 229 provides the FMA address required for commitment of each of the registers and the source of the data to be written when the FMC register is written with a value of 0xA442.0008. After writing the COMT bit, the user may poll the FMC register to wait for the commit operation to complete.

Table 6-2. User-Programmable Flash Memory Resident Registers

Register to be Committed	FMA Value	Data Source
FMPRE0	0x0000.0000	FMPRE0
FMPRE1	0x0000.0002	FMPRE1
FMPPE0	0x0000.0001	FMPPE0
FMPPE1	0x0000.0003	FMPPE1
USER_REG0	0x8000.0000	USER_REG0
USER_REG1	0x8000.0001	USER_REG1
USER_REG2	0x8000.0002	USER_REG2
USER_REG3	0x8000.0003	USER_REG3
USER_DBG	0x7510.0000	FMD

# 6.4 Register Map

Table 6-3 on page 229 lists the Flash memory and control registers. The offset listed is a hexadecimal increment to the register's address. The **FMA**, **FMD**, **FMC**, **FCRIS**, **FCIM**, and **FCMISC** register offsets are relative to the Flash memory control base address of 0x400F.D000. The Flash memory protection register offsets are relative to the System Control base address of 0x400F.E000.

Table 6-3. Flash Register Map

Offset	Name	Туре	Reset	Description	See page
Flash Me	mory Control Register	s (Flash Cont	rol Offset)		
0x000	FMA	R/W	0x0000.0000	Flash Memory Address	231
0x004	FMD	R/W	0x0000.0000	Flash Memory Data	232
0x008	FMC	R/W	0x0000.0000	Flash Memory Control	233
0x00C	FCRIS	RO	0x0000.0000	Flash Controller Raw Interrupt Status	235
0x010	FCIM	R/W	0x0000.0000	Flash Controller Interrupt Mask	236
0x014	FCMISC	R/W1C	0x0000.0000	Flash Controller Masked Interrupt Status and Clear	237
Flash Me	mory Protection Regis	ters (System	Control Offset)		
0x130	FMPRE0	R/W	0xFFFF.FFFF	Flash Memory Protection Read Enable 0	240
0x200	FMPRE0	R/W	0xFFFF.FFFF	Flash Memory Protection Read Enable 0	240
0x134	FMPPE0	R/W	0xFFFF.FFFF	Flash Memory Protection Program Enable 0	241
0x400	FMPPE0	R/W	0xFFFF.FFFF	Flash Memory Protection Program Enable 0	241
0x140	USECRL	R/W	0x18	USec Reload	239
0x1D0	USER_DBG	R/W	0xFFFF.FFFE	User Debug	242
0x1E0	USER_REG0	R/W	0xFFFF.FFFF	User Register 0	243
0x1E4	USER_REG1	R/W	0xFFFF.FFFF	User Register 1	244
0x204	FMPRE1	R/W	0x0000.FFFF	Flash Memory Protection Read Enable 1	245
0x208	FMPRE2	R/W	0x0000.0000	Flash Memory Protection Read Enable 2	246

Table 6-3. Flash Register Map (continued)

Offset	Name	Type	Reset	Description	See page
0x20C	FMPRE3	R/W	0x0000.0000	Flash Memory Protection Read Enable 3	247
0x404	FMPPE1	R/W	0x0000.FFFF	Flash Memory Protection Program Enable 1	248
0x408	FMPPE2	R/W	0x0000.0000	Flash Memory Protection Program Enable 2	249
0x40C	FMPPE3	R/W	0x0000.0000	Flash Memory Protection Program Enable 3	250

# 6.5 Flash Register Descriptions (Flash Control Offset)

This section lists and describes the Flash Memory registers, in numerical order by address offset. Registers in this section are relative to the Flash control base address of 0x400F.D000.

## Register 1: Flash Memory Address (FMA), offset 0x000


During a write operation, this register contains a 4-byte-aligned address and specifies where the data is written. During erase operations, this register contains a 1 KB-aligned address and specifies which page is erased. Note that the alignment requirements must be met by software or the results of the operation are unpredictable.

Flash Memory Address (FMA)

Base 0x400F.D000

31:17

Offset 0x000 Type R/W, reset 0x0000.0000



compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.

0x0

16:0 OFFSET R/W 0x0 Address Offset

RO

reserved

Address offset in flash where operation is performed, except for nonvolatile registers (see "Nonvolatile Register Programming" on page 228 for details on values for this field).

Software should not rely on the value of a reserved bit. To provide


# Register 2: Flash Memory Data (FMD), offset 0x004

This register contains the data to be written during the programming cycle or read during the read cycle. Note that the contents of this register are undefined for a read access of an execute-only block. This register is not used during the erase cycles.

Flash Memory Data (FMD)

Base 0x400F.D000

Offset 0x004 Type R/W, reset 0x0000.0000



Bit/Field Name Type Reset Description
31:0 DATA R/W 0x0 Data Value

Data value for write operation.

## Register 3: Flash Memory Control (FMC), offset 0x008

When this register is written, the flash controller initiates the appropriate access cycle for the location specified by the **Flash Memory Address (FMA)** register (see page 231). If the access is a write access, the data contained in the **Flash Memory Data (FMD)** register (see page 232) is written.

This is the final register written and initiates the memory operation. There are four control bits in the lower byte of this register that, when set, initiate the memory operation. The most used of these register bits are the ERASE and WRITE bits.

It is a programming error to write multiple control bits and the results of such an operation are unpredictable.

#### Flash Memory Control (FMC)

Base 0x400F.D000 Offset 0x008


2

**MERASE** 

R/W

0

Type R/W, reset 0x0000.0000



Bit/Field	Name	Type	Reset	Description
31:16	WRKEY	WO	0x0	Flash Write Key  This field contains a write key, which is used to minimize the incidence of accidental flash writes. The value 0xA442 must be written into this field for a write to occur. Writes to the <b>FMC</b> register without this WRKEY value are ignored. A read of this field returns the value 0.
15:4	reserved	RO	0x0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
3	COMT	R/W	0	Commit Register Value
				Commit (write) of register value to nonvolatile storage. A write of 0 has no effect on the state of this bit.
				If read, the state of the previous commit access is provided. If the previous commit access is complete, a 0 is returned; otherwise, if the commit access is not complete, a 1 is returned.
				This can take up to 50 μs.

If this bit is set, the flash main memory of the device is all erased. A write of 0 has no effect on the state of this bit.

If read, the state of the previous mass erase access is provided. If the previous mass erase access is complete, a 0 is returned; otherwise, if the previous mass erase access is not complete, a 1 is returned.

This can take up to 250 ms.

Mass Erase Flash Memory

Bit/Field	Name	Type	Reset	Description
1	ERASE	R/W	0	Erase a Page of Flash Memory
				If this bit is set, the page of flash main memory as specified by the contents of <b>FMA</b> is erased. A write of 0 has no effect on the state of this bit.
				If read, the state of the previous erase access is provided. If the previous erase access is complete, a 0 is returned; otherwise, if the previous erase access is not complete, a 1 is returned.
				This can take up to 25 ms.
0	WRITE	R/W	0	Write a Word into Flash Memory
				If this bit is set, the data stored in <b>FMD</b> is written into the location as specified by the contents of <b>FMA</b> . A write of 0 has no effect on the state of this bit.
				If read, the state of the previous write update is provided. If the previous write access is complete, a 0 is returned; otherwise, if the write access is not complete, a 1 is returned.
				This can take up to 50 μs.


## Register 4: Flash Controller Raw Interrupt Status (FCRIS), offset 0x00C

This register indicates that the flash controller has an interrupt condition. An interrupt is only signaled if the corresponding **FCIM** register bit is set.

Flash Controller Raw Interrupt Status (FCRIS)

Base 0x400F.D000

Offset 0x00C Type RO, reset 0x0000.0000



Bit/Field	Name	Type	Reset	Description
31:2	reserved	RO	0x0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
1	PRIS	RO	0	Programming Raw Interrupt Status
				This bit provides status on programming cycles which are write or erase actions generated through the <b>FMC</b> register bits (see page 233).

#### Value Description

- 1 The programming cycle has completed.
- 0 The programming cycle has not completed.

This status is sent to the interrupt controller when the  ${\tt PMASK}$  bit in the FCIM register is set.

This bit is cleared by writing a 1 to the PMISC bit in the **FCMISC** register.

0 ARIS RO 0 Access Raw Interrupt Status

#### Value Description

- A program or erase action was attempted on a block of Flash memory that contradicts the protection policy for that block as set in the FMPPEn registers.
- 0 No access has tried to improperly program or erase the Flash memory.

This status is sent to the interrupt controller when the  ${\tt AMASK}$  bit in the FCIM register is set.

This bit is cleared by writing a 1 to the AMISC bit in the FCMISC register.

# Register 5: Flash Controller Interrupt Mask (FCIM), offset 0x010

This register controls whether the flash controller generates interrupts to the controller.

Flash Controller Interrupt Mask (FCIM)

Base 0x400F.D000 Offset 0x010


0

AMASK

R/W

0

Type R/W, reset 0x0000.0000



Bit/Field	Name	Туре	Reset	Description
31:2	reserved	RO	0x0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
1	PMASK	R/W	0	Programming Interrupt Mask
				This bit controls the reporting of the programming raw interrupt status to the interrupt controller.
				Value Description
				1 An interrupt is sent to the interrupt controller when the PRIS bit is set.
				O The PRIS interrupt is suppressed and not sent to the interrupt controller.

# Access Interrupt Mask

This bit controls the reporting of the access raw interrupt status to the interrupt controller.

#### Value Description

- 1 An interrupt is sent to the interrupt controller when the ARIS bit is set.
- 0 The ARIS interrupt is suppressed and not sent to the interrupt controller.


### Register 6: Flash Controller Masked Interrupt Status and Clear (FCMISC), offset 0x014

This register provides two functions. First, it reports the cause of an interrupt by indicating which interrupt source or sources are signalling the interrupt. Second, it serves as the method to clear the interrupt reporting.

Flash Controller Masked Interrupt Status and Clear (FCMISC)

Base 0x400F.D000

Offset 0x014
Type R/W1C, reset 0x0000.0000



31:2	reserved	RO	0x0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
1	PMISC	R/W1C	0	Programming Masked Interrupt Status and Clear

#### Value Description

- 1 When read, a 1 indicates that an unmasked interrupt was signaled because a programming cycle completed.
  - Writing a 1 to this bit clears PMISC and also the PRIS bit in the FCRIS register (see page 235).
- When read, a 0 indicates that a programming cycle complete 0 interrupt has not occurred.

A write of 0 has no effect on the state of this bit.

0	AMISC	R/W1C	0	Access Masked Interrupt Status and Clear
---	-------	-------	---	--

#### Value Description

- When read, a 1 indicates that an unmasked interrupt was signaled because a program or erase action was attempted on a block of Flash memory that contradicts the protection policy for that block as set in the FMPPEn registers.
  - Writing a 1 to this bit clears AMISC and also the ARIS bit in the FCRIS register (see page 235).
- 0 When read, a 0 indicates that no improper accesses have occurred.

A write of 0 has no effect on the state of this bit.

# 6.6 Flash Register Descriptions (System Control Offset)

The remainder of this section lists and describes the Flash Memory registers, in numerical order by address offset. Registers in this section are relative to the System Control base address of 0x400F.E000.

## Register 7: USec Reload (USECRL), offset 0x140


Note: Offset is relative to System Control base address of 0x400F.E000

This register is provided as a means of creating a 1-µs tick divider reload value for the flash controller. The internal flash has specific minimum and maximum requirements on the length of time the high voltage write pulse can be applied. It is required that this register contain the operating frequency (in MHz -1) whenever the flash is being erased or programmed. The user is required to change this value if the clocking conditions are changed for a flash erase/program operation.

#### USec Reload (USECRL)

Base 0x400F.E000 Offset 0x140 Type R/W, reset 0x18

D://E: 1.1



Bit/Field	Name	туре	Reset	Description
31:8	reserved	RO	0x0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
7:0	USEC	R/W	0x18	Microsecond Reload Value

MHz -1 of the controller clock when the flash is being erased or programmed.

If the maximum system frequency is being used, USEC should be set to 0x18 (24 MHz) whenever the flash is being erased or programmed.

# Register 8: Flash Memory Protection Read Enable 0 (FMPRE0), offset 0x130 and 0x200


Note: This register is aliased for backwards compatability.

Note: Offset is relative to System Control base address of 0x400FE000.

This register stores the read-only protection bits for each 2-KB flash block (**FMPPEn** stores the execute-only bits). Flash memory up to a total of 64 KB is controlled by this register. Other **FMPREn** registers (if any) provide protection for other 64K blocks. This register is loaded during the power-on reset sequence. The factory settings for the **FMPREn** and **FMPPEn** registers are a value of 1 for all implemented banks. This achieves a policy of open access and programmability. The register bits may be changed by writing the specific register bit. However, this register is R/W0; the user can only change the protection bit from a 1 to a 0 (and may NOT change a 0 to a 1). The changes are not permanent until the register is committed (saved), at which point the bit change is permanent. If a bit is changed from a 1 to a 0 and not committed, it may be restored by executing a power-on reset sequence. The reset value shown only applies to power-on reset; any other type of reset does not affect this register. For additional information, see the "Flash Memory Protection" section.

Flash Memory Protection Read Enable 0 (FMPRE0)

Base 0x400F.E000 Offset 0x130 and 0x200 Type R/W, reset 0xFFFF.FFFF



Bit/Field Name Type Reset Description

31:0 READ\_ENABLE R/W 0xFFFFFFF Flash Read Enable. Enables 2-KB Flash memory blocks to be executed or read. The policies may be combined as shown in the table "Flash Protection Policy Combinations".

Value Description

0xFFFFFFF Bits [31:0] each enable protection on a 2-KB block of Flash memory up to the total of 64 KB.

# Register 9: Flash Memory Protection Program Enable 0 (FMPPE0), offset 0x134 and 0x400


Note: This register is aliased for backwards compatability.

**Note:** Offset is relative to System Control base address of 0x400FE000.

This register stores the execute-only protection bits for each 2-KB flash block (**FMPREn** stores the execute-only bits). Flash memory up to a total of 64 KB is controlled by this register. Other **FMPPEn** registers (if any) provide protection for other 64K blocks. This register is loaded during the power-on reset sequence. The factory settings for the **FMPREn** and **FMPPEn** registers are a value of 1 for all implemented banks. This achieves a policy of open access and programmability. The register bits may be changed by writing the specific register bit. However, this register is R/W0; the user can only change the protection bit from a 1 to a 0 (and may NOT change a 0 to a 1). The changes are not permanent until the register is committed (saved), at which point the bit change is permanent. If a bit is changed from a 1 to a 0 and not committed, it may be restored by executing a power-on reset sequence. The reset value shown only applies to power-on reset; any other type of reset does not affect this register. For additional information, see the "Flash Memory Protection" section.

Flash Memory Protection Program Enable 0 (FMPPE0)

Base 0x400F.E000 Offset 0x134 and 0x400 Type R/W, reset 0xFFFF.FFFF



Bit/Field Name Type Reset Description

31:0 PROG\_ENABLE R/W 0xFFFFFFF Flash Programming Enable

Configures 2-KB flash blocks to be execute only. The policies may be combined as shown in the table "Flash Protection Policy Combinations".

Value Description

0xFFFFFFF Bits [31:0] each enable protection on a 2-KB block of Flash memory up to the total of 64 KB.

## Register 10: User Debug (USER\_DBG), offset 0x1D0


**Note:** Offset is relative to System Control base address of 0x400FE000.

This register provides a write-once mechanism to disable external debugger access to the device in addition to 27 additional bits of user-defined data. The DBG0 bit (bit 0) is set to 0 from the factory and the DBG1 bit (bit 1) is set to 1, which enables external debuggers. Changing the DBG1 bit to 0 disables any external debugger access to the device permanently, starting with the next power-up cycle of the device. The NW bit (bit 31) indicates that the register has not yet been committed and is controlled through hardware to ensure that the register is only committed once. Prior to being committed, bits can only be changed from 1 to 0. The reset value shown only applies to power-on reset; any other type of reset does not affect this register. Once committed, this register cannot be restored to the factory default value.

#### User Debug (USER\_DBG)

Base 0x400F.E000 Offset 0x1D0

Type R/W, reset 0xFFFF.FFFE



Bit/Field	Name	Туре	Reset	Description
31	NW	R/W	1	User Debug Not Written When set, this bit indicates that this 32-bit register has not been committed. When clear, this bit specifies that this register has been committed and may not be committed again.
30:2	DATA	R/W	0x1FFFFFFF	User Data  Contains the user data value. This field is initialized to all 1s and can only be committed once.
1	DBG1	R/W	1	Debug Control 1  The DBG1 bit must be 1 and DBG0 must be 0 for debug to be available.
0	DBG0	R/W	0	Debug Control 0 The DBG1 bit must be 1 and DBG0 must be 0 for debug to be available.

## Register 11: User Register 0 (USER\_REG0), offset 0x1E0


**Note:** Offset is relative to System Control base address of 0x400FE000.

This register provides 31 bits of user-defined data that is non-volatile and can only be committed once. Bit 31 indicates that the register is available to be committed and is controlled through hardware to ensure that the register is only committed once. Prior to being committed, bits can only be changed from 1 to 0. The reset value shown only applies to power-on reset; any other type of reset does not affect this register. The write-once characteristics of this register are useful for keeping static information like communication addresses that need to be unique per part and would otherwise require an external EEPROM or other non-volatile device. Once committed, this register cannot be restored to the factory default value.

#### User Register 0 (USER\_REG0)

Base 0x400F.E000 Offset 0x1E0

Type R/W, reset 0xFFFF.FFFF



Bit/Field	Name	Туре	Reset	Description
31	NW	R/W	1	Not Written
				When set, this bit indicates that this 32-bit register has not been committed. When clear, this bit specifies that this register has been committed and may not be committed again.
30:0	DATA	R/W 0x	7FFFFFF	User Data

Contains the user data value. This field is initialized to all 1s and can only be committed once.

## Register 12: User Register 1 (USER\_REG1), offset 0x1E4


**Note:** Offset is relative to System Control base address of 0x400FE000.

This register provides 31 bits of user-defined data that is non-volatile and can only be committed once. Bit 31 indicates that the register is available to be committed and is controlled through hardware to ensure that the register is only committed once. Prior to being committed, bits can only be changed from 1 to 0. The reset value shown only applies to power-on reset; any other type of reset does not affect this register. The write-once characteristics of this register are useful for keeping static information like communication addresses that need to be unique per part and would otherwise require an external EEPROM or other non-volatile device. Once committed, this register cannot be restored to the factory default value.

User Register 1 (USER REG1)

Base 0x400F.E000 Offset 0x1E4

Type R/W, reset 0xFFFF.FFFF



Bit/Field	Name	Туре	Reset	Description
31	NW	R/W	1	Not Written When set, this bit indicates that this 32-bit register has not been
				committed. When clear, this bit specifies that this register has been committed and may not be committed again.
30:0	DATA	R/W 0x	7FFFFFF	User Data

Contains the user data value. This field is initialized to all 1s and can only be committed once.

### Register 13: Flash Memory Protection Read Enable 1 (FMPRE1), offset 0x204


**Note:** Offset is relative to System Control base address of 0x400FE000.

This register stores the read-only protection bits for each 2-KB flash block (**FMPPEn** stores the execute-only bits). Flash memory up to a total of 64 KB is controlled by this register. Other **FMPREn** registers (if any) provide protection for other 64K blocks. This register is loaded during the power-on reset sequence. The factory settings for the **FMPREn** and **FMPPEn** registers are a value of 1 for all implemented banks. This achieves a policy of open access and programmability. The register bits may be changed by writing the specific register bit. However, this register is R/W0; the user can only change the protection bit from a 1 to a 0 (and may NOT change a 0 to a 1). The changes are not permanent until the register is committed (saved), at which point the bit change is permanent. If a bit is changed from a 1 to a 0 and not committed, it may be restored by executing a power-on reset sequence. The reset value shown only applies to power-on reset; any other type of reset does not affect this register. If the Flash memory size on the device is less than 64 KB, this register usually reads as zeroes, but software should not rely on these bits to be zero. For additional information, see the "Flash Memory Protection" section.

Flash Memory Protection Read Enable 1 (FMPRE1)

Base 0x400F.E000 Offset 0x204

Type R/W, reset 0x0000.FFFF



Bit/Field Name Type Reset Description

31:0 READ ENABLE R/W 0x0000FFFF Flash Read

Flash Read Enable. Enables 2-KB Flash memory blocks to be executed or read. The policies may be combined as shown in the table "Flash Protection Policy Combinations".

Value Description

0x0000FFFF Bits [31:0] each enable protection on a 2-KB block of Flash memory in memory range from 65 to 128 KB.


### Register 14: Flash Memory Protection Read Enable 2 (FMPRE2), offset 0x208

Note: Offset is relative to System Control base address of 0x400FE000.

This register stores the read-only protection bits for each 2-KB flash block (**FMPPEn** stores the execute-only bits). This register is loaded during the power-on reset sequence. The factory settings for the **FMPREn** and **FMPPEn** registers are a value of 1 for all implemented banks. This achieves a policy of open access and programmability. The register bits may be changed by writing the specific register bit. However, this register is R/W0; the user can only change the protection bit from a 1 to a 0 (and may NOT change a 0 to a 1). For additional information, see the "Flash Memory Protection" section.

Flash Memory Protection Read Enable 2 (FMPRE2)

Base 0x400F.E000 Offset 0x208 Type R/W, reset 0x0000.0000



31:0 READ ENABLE R/W 0x00000000 Flash Read Enable

Enables 2-KB flash blocks to be executed or read. The policies may be combined as shown in the table "Flash Protection Policy Combinations".

Value Description

0x00000000 Enables 96 KB of flash.

## Register 15: Flash Memory Protection Read Enable 3 (FMPRE3), offset 0x20C


**Note:** Offset is relative to System Control base address of 0x400FE000.

This register stores the read-only protection bits for each 2-KB flash block (**FMPPEn** stores the execute-only bits). This register is loaded during the power-on reset sequence. The factory settings for the **FMPREn** and **FMPPEn** registers are a value of 1 for all implemented banks. This achieves a policy of open access and programmability. The register bits may be changed by writing the specific register bit. However, this register is R/W0; the user can only change the protection bit from a 1 to a 0 (and may NOT change a 0 to a 1). The changes are not permanent until the register is committed (saved), at which point the bit change is permanent. If a bit is changed from a 1 to a 0 and not committed, it may be restored by executing a power-on reset sequence. For additional information, see the "Flash Memory Protection" section.

Flash Memory Protection Read Enable 3 (FMPRE3)

Base 0x400F.E000 Offset 0x20C

Type R/W, reset 0x0000.0000



Bit/Field Name Type Reset Description

31:0 READ\_ENABLE R/W 0x00000000 Flash Read Enable

Enables 2-KB flash blocks to be executed or read. The policies may be combined as shown in the table "Flash Protection Policy Combinations".

Value Description

0x00000000 Enables 96 KB of flash.

# Register 16: Flash Memory Protection Program Enable 1 (FMPPE1), offset 0x404


**Note:** Offset is relative to System Control base address of 0x400FE000.

This register stores the execute-only protection bits for each 2-KB flash block (**FMPREn** stores the execute-only bits). Flash memory up to a total of 64 KB is controlled by this register. Other **FMPPEn** registers (if any) provide protection for other 64K blocks. This register is loaded during the power-on reset sequence. The factory settings for the **FMPREn** and **FMPPEn** registers are a value of 1 for all implemented banks. This achieves a policy of open access and programmability. The register bits may be changed by writing the specific register bit. However, this register is R/W0; the user can only change the protection bit from a 1 to a 0 (and may NOT change a 0 to a 1). The changes are not permanent until the register is committed (saved), at which point the bit change is permanent. If a bit is changed from a 1 to a 0 and not committed, it may be restored by executing a power-on reset sequence. The reset value shown only applies to power-on reset; any other type of reset does not affect this register. If the Flash memory size on the device is less than 64 KB, this register usually reads as zeroes, but software should not rely on these bits to be zero. For additional information, see the "Flash Memory Protection" section.

Flash Memory Protection Program Enable 1 (FMPPE1)

Base 0x400F.E000 Offset 0x404

Type R/W, reset 0x0000.FFFF



Bit/Field Name Type Reset Description

31:0 PROG\_ENABLE R/W 0x0000FFFF Flash Programming Enable

Value Description

0x0000FFFF Bits [31:0] each enable protection on a 2-KB block of Flash memory in memory range from 65 to 128 KB.

# Register 17: Flash Memory Protection Program Enable 2 (FMPPE2), offset 0x408


**Note:** Offset is relative to System Control base address of 0x400FE000.

This register stores the execute-only protection bits for each 2-KB flash block (**FMPREn** stores the execute-only bits). This register is loaded during the power-on reset sequence. The factory settings for the **FMPREn** and **FMPPEn** registers are a value of 1 for all implemented banks. This achieves a policy of open access and programmability. The register bits may be changed by writing the specific register bit. However, this register is R/W0; the user can only change the protection bit from a 1 to a 0 (and may NOT change a 0 to a 1). The changes are not permanent until the register is committed (saved), at which point the bit change is permanent. If a bit is changed from a 1 to a 0 and not committed, it may be restored by executing a power-on reset sequence. For additional information, see the "Flash Memory Protection" section.

Flash Memory Protection Program Enable 2 (FMPPE2)

Base 0x400F.E000 Offset 0x408

Type R/W, reset 0x0000.0000



Bit/Field Name Type Reset Description

31:0 PROG\_ENABLE R/W 0x00000000 Flash Programming Enable

Configures 2-KB flash blocks to be execute only. The policies may be combined as shown in the table "Flash Protection Policy Combinations".

Value Description

0x00000000 Enables 96 KB of flash.

November 18, 2011 249

# Register 18: Flash Memory Protection Program Enable 3 (FMPPE3), offset 0x40C


**Note:** Offset is relative to System Control base address of 0x400FE000.

This register stores the execute-only protection bits for each 2-KB flash block (**FMPREn** stores the execute-only bits). This register is loaded during the power-on reset sequence. The factory settings for the **FMPREn** and **FMPPEn** registers are a value of 1 for all implemented banks. This achieves a policy of open access and programmability. The register bits may be changed by writing the specific register bit. However, this register is R/W0; the user can only change the protection bit from a 1 to a 0 (and may NOT change a 0 to a 1). The changes are not permanent until the register is committed (saved), at which point the bit change is permanent. If a bit is changed from a 1 to a 0 and not committed, it may be restored by executing a power-on reset sequence. For additional information, see the "Flash Memory Protection" section.

Flash Memory Protection Program Enable 3 (FMPPE3)

Base 0x400F.E000 Offset 0x40C

Type R/W, reset 0x0000.0000



Bit/Field Name Type Reset Description

31:0 PROG\_ENABLE R/W 0x00000000 Flash Programming Enable

Configures 2-KB flash blocks to be execute only. The policies may be combined as shown in the table "Flash Protection Policy Combinations".

Value Description

0x00000000 Enables 96 KB of flash.

# 7 General-Purpose Input/Outputs (GPIOs)

The GPIO module is composed of seven physical GPIO blocks, each corresponding to an individual GPIO port (Port A, Port B, Port C, Port D, Port E, Port F, Port G). The GPIO module supports 12-34 programmable input/output pins, depending on the peripherals being used.

The GPIO module has the following features:

- 12-34 GPIOs, depending on configuration
- 5-V-tolerant in input configuration
- Fast toggle capable of a change every two clock cycles
- Programmable control for GPIO interrupts
  - Interrupt generation masking
  - Edge-triggered on rising, falling, or both
  - Level-sensitive on High or Low values
- Bit masking in both read and write operations through address lines
- Can initiate an ADC sample sequence
- Pins configured as digital inputs are Schmitt-triggered.
- Programmable control for GPIO pad configuration
  - Weak pull-up or pull-down resistors
  - 2-mA, 4-mA, and 8-mA pad drive for digital communication; up to four pads can be configured with an 18-mA pad drive for high-current applications
  - Slew rate control for the 8-mA drive
  - Open drain enables
  - Digital input enables

# 7.1 Signal Description

GPIO signals have alternate hardware functions. Table 7-4 on page 254 and Table 7-5 on page 254 list the GPIO pins and the analog and digital alternate functions. The AINx analog signals are not 5-V tolerant and go through an isolation circuit before reaching their circuitry. These signals are configured by clearing the corresponding DEN bit in the GPIO Digital Enable (GPIODEN) register and setting the corresponding AMSEL bit in the GPIO Analog Mode Select (GPIOAMSEL) register. Other analog signals are 5-V tolerant and are connected directly to their circuitry (CO-, CO+, C1-, C1+). These signals are configured by clearing the DEN bit in the GPIO Digital Enable (GPIODEN) register. The digital alternate hardware functions are enabled by setting the appropriate bit in the GPIO Alternate Function Select (GPIOAFSEL) and GPIODEN registers and configuring the PMCx bit field in the GPIO Port Control (GPIOPCTL) register to the numeric enoding shown in the table below. Note that each pin must be programmed individually; no type of grouping is implied by the columns in the table.

Important: All GPIO pins are configured as GPIOs and tri-stated by default (GPIOAFSEL=0, GPIODEN=0, GPIOPDR=0, GPIOPUR=0, and GPIOPCTL=0, with the exception of the four JTAG/SWD pins (shown in the table below). A Power-On-Reset (POR) or asserting RST puts the pins back to their default state.

Table 7-1. GPIO Pins With Non-Zero Reset Values

GPIO Pins	Default State	GPIOAFSEL	GPIODEN	GPIOPDR	GPIOPUR	GPIOPCTL
PA[1:0]	UART0	1	1	0	0	0x1
PA[5:2]	SSI0	1	1	0	0	0x1
PC[3:0]	JTAG/SWD	1	1	0	1	0x3

Table 7-2. GPIO Pins and Alternate Functions (100LQFP)

10	Pin Number	Multiplexed Function	Multiplexed Function
PA0	26	UORx	
PA1	27	UOTx	
PA2	28	SSIOClk	
PA3	29	SSI0Fss	
PA4	30	SSIORx	
PA5	31	SSIOTX	
PA6	34	CCP1	
PB0	66	CCP0	
PB1	67	CCP2	
PB2	70		
PB3	71		
PB4	92	C0-	
PB5	91	C1-	
PB6	90	C0+	
PB7	89	TRST	
PC0	80	TCK	SWCLK
PC1	79	TMS	SWDIO
PC2	78	TDI	
PC3	77	TDO	SWO
PC4	25		
PC5	24	C1+	Clo
PC6	23	CCP3	
PD0	10		
PD1	11		
PD2	12		
PD3	13		
PD4	95		
PD5	96		
PD6	99		
PD7	100	C0o	

Table 7-2. GPIO Pins and Alternate Functions (100LQFP) (continued)

10	Pin Number	Multiplexed Function	Multiplexed Function
PF0	47		
PF1	61		
PF2	60	LED1	
PF3	59	LED0	

Table 7-3. GPIO Pins and Alternate Functions (108BGA)

10	Pin Number	Multiplexed Function	Multiplexed Function
PA0	L3	U0Rx	
PA1	M3	UOTx	
PA2	M4	SSI0Clk	
PA3	L4	SSI0Fss	
PA4	L5	SSI0Rx	
PA5	M5	SSIOTx	
PA6	L6	CCP1	
PB0	E12	CCP0	
PB1	D12	CCP2	
PB2	C11		
PB3	C12		
PB4	A6	C0-	
PB5	B7	C1-	
PB6	A7	C0+	
PB7	A8	TRST	
PC0	A9	TCK	SWCLK
PC1	B9	TMS	SWDIO
PC2	B8	TDI	
PC3	A10	TDO	SWO
PC4	L1		
PC5	M1	C1+	C1o
PC6	M2	CCP3	
PD0	G1		
PD1	G2		
PD2	H2		
PD3	H1		
PD4	E1		
PD5	E2		
PD6	F2		
PD7	F1	C0o	
PF0	M9		
PF1	H12		
PF2	J11	LED1	
PF3	J12	LED0	

Table 7-4. GPIO Signals (100LQFP)

Pin Name	Pin Number	Pin Type	Buffer Type <sup>a</sup>	Description
PA0	26	I/O	TTL	GPIO port A bit 0.
PA1	27	I/O	TTL	GPIO port A bit 1.
PA2	28	I/O	TTL	GPIO port A bit 2.
PA3	29	I/O	TTL	GPIO port A bit 3.
PA4	30	I/O	TTL	GPIO port A bit 4.
PA5	31	I/O	TTL	GPIO port A bit 5.
PA6	34	I/O	TTL	GPIO port A bit 6.
PB0	66	I/O	TTL	GPIO port B bit 0.
PB1	67	I/O	TTL	GPIO port B bit 1.
PB2	70	I/O	TTL	GPIO port B bit 2.
PB3	71	I/O	TTL	GPIO port B bit 3.
PB4	92	I/O	TTL	GPIO port B bit 4.
PB5	91	I/O	TTL	GPIO port B bit 5.
PB6	90	I/O	TTL	GPIO port B bit 6.
PB7	89	I/O	TTL	GPIO port B bit 7.
PC0	80	I/O	TTL	GPIO port C bit 0.
PC1	79	I/O	TTL	GPIO port C bit 1.
PC2	78	I/O	TTL	GPIO port C bit 2.
PC3	77	I/O	TTL	GPIO port C bit 3.
PC4	25	I/O	TTL	GPIO port C bit 4.
PC5	24	I/O	TTL	GPIO port C bit 5.
PC6	23	I/O	TTL	GPIO port C bit 6.
PD0	10	I/O	TTL	GPIO port D bit 0.
PD1	11	I/O	TTL	GPIO port D bit 1.
PD2	12	I/O	TTL	GPIO port D bit 2.
PD3	13	I/O	TTL	GPIO port D bit 3.
PD4	95	I/O	TTL	GPIO port D bit 4.
PD5	96	I/O	TTL	GPIO port D bit 5.
PD6	99	I/O	TTL	GPIO port D bit 6.
PD7	100	I/O	TTL	GPIO port D bit 7.
PF0	47	I/O	TTL	GPIO port F bit 0.
PF1	61	I/O	TTL	GPIO port F bit 1.
PF2	60	I/O	TTL	GPIO port F bit 2.
PF3	59	I/O	TTL	GPIO port F bit 3.

a. The TTL designation indicates the pin has TTL-compatible voltage levels.

# Table 7-5. GPIO Signals (108BGA)

Pin Name	Pin Number	Pin Type	Buffer Type <sup>a</sup>	Description
PA0	L3	I/O	TTL	GPIO port A bit 0.
PA1	M3	I/O	TTL	GPIO port A bit 1.
PA2	M4	I/O	TTL	GPIO port A bit 2.

Table 7-5. GPIO Signals (108BGA) (continued)

Pin Name	Pin Number	Pin Type	Buffer Type <sup>a</sup>	Description
PA3	L4	I/O	TTL	GPIO port A bit 3.
PA4	L5	I/O	TTL	GPIO port A bit 4.
PA5	M5	I/O	TTL	GPIO port A bit 5.
PA6	L6	I/O	TTL	GPIO port A bit 6.
PB0	E12	I/O	TTL	GPIO port B bit 0.
PB1	D12	I/O	TTL	GPIO port B bit 1.
PB2	C11	I/O	TTL	GPIO port B bit 2.
PB3	C12	I/O	TTL	GPIO port B bit 3.
PB4	A6	I/O	TTL	GPIO port B bit 4.
PB5	B7	I/O	TTL	GPIO port B bit 5.
PB6	A7	I/O	TTL	GPIO port B bit 6.
PB7	A8	I/O	TTL	GPIO port B bit 7.
PC0	A9	I/O	TTL	GPIO port C bit 0.
PC1	В9	I/O	TTL	GPIO port C bit 1.
PC2	В8	I/O	TTL	GPIO port C bit 2.
PC3	A10	I/O	TTL	GPIO port C bit 3.
PC4	L1	I/O	TTL	GPIO port C bit 4.
PC5	M1	I/O	TTL	GPIO port C bit 5.
PC6	M2	I/O	TTL	GPIO port C bit 6.
PD0	G1	I/O	TTL	GPIO port D bit 0.
PD1	G2	I/O	TTL	GPIO port D bit 1.
PD2	H2	I/O	TTL	GPIO port D bit 2.
PD3	H1	I/O	TTL	GPIO port D bit 3.
PD4	E1	I/O	TTL	GPIO port D bit 4.
PD5	E2	I/O	TTL	GPIO port D bit 5.
PD6	F2	I/O	TTL	GPIO port D bit 6.
PD7	F1	I/O	TTL	GPIO port D bit 7.
PF0	M9	I/O	TTL	GPIO port F bit 0.
PF1	H12	I/O	TTL	GPIO port F bit 1.
PF2	J11	I/O	TTL	GPIO port F bit 2.
PF3	J12	I/O	TTL	GPIO port F bit 3.

a. The TTL designation indicates the pin has TTL-compatible voltage levels.

# 7.2 Functional Description


Important: All GPIO pins are tri-stated by default (GPIOAFSEL=0, GPIODEN=0, GPIOPDR=0, and GPIOPUR=0), with the exception of the five JTAG/SWD pins (PB7 and PC[3:0]). The JTAG/SWD pins default to their JTAG/SWD functionality (GPIOAFSEL=1, GPIODEN=1 and GPIOPUR=1). A Power-On-Reset (POR) or asserting RST puts both groups of pins back to their default state.

While debugging systems where PB7 is being used as a GPIO, care must be taken to ensure that a low value is not applied to the pin when the part is reset. Because PB7

reverts to the TRST function after reset, a Low value on the pin causes the JTAG controller to be reset, resulting in a loss of JTAG communication.

Each GPIO port is a separate hardware instantiation of the same physical block (see Figure 7-1 on page 256). The LM3S6422 microcontroller contains seven ports and thus seven of these physical GPIO blocks.

Figure 7-1. GPIO Port Block Diagram



### 7.2.1 Data Control

The data control registers allow software to configure the operational modes of the GPIOs. The data direction register configures the GPIO as an input or an output while the data register either captures incoming data or drives it out to the pads.

### 7.2.1.1 Data Direction Operation

The **GPIO Direction (GPIODIR)** register (see page 264) is used to configure each individual pin as an input or output. When the data direction bit is set to 0, the GPIO is configured as an input and the corresponding data register bit will capture and store the value on the GPIO port. When the data direction bit is set to 1, the GPIO is configured as an output and the corresponding data register bit will be driven out on the GPIO port.


### 7.2.1.2 Data Register Operation

To aid in the efficiency of software, the GPIO ports allow for the modification of individual bits in the **GPIO Data (GPIODATA)** register (see page 263) by using bits [9:2] of the address bus as a mask. This allows software drivers to modify individual GPIO pins in a single instruction, without affecting the state of the other pins. This is in contrast to the "typical" method of doing a read-modify-write operation to set or clear an individual GPIO pin. To accommodate this feature, the **GPIODATA** register covers 256 locations in the memory map.

During a write, if the address bit associated with that data bit is set to 1, the value of the **GPIODATA** register is altered. If it is cleared to 0, it is left unchanged.


For example, writing a value of 0xEB to the address GPIODATA + 0x098 would yield as shown in Figure 7-2 on page 257, where u is data unchanged by the write.

Figure 7-2. GPIODATA Write Example



During a read, if the address bit associated with the data bit is set to 1, the value is read. If the address bit associated with the data bit is set to 0, it is read as a zero, regardless of its actual value. For example, reading address GPIODATA + 0x0C4 yields as shown in Figure 7-3 on page 257.

Figure 7-3. GPIODATA Read Example



### 7.2.2 Interrupt Control

The interrupt capabilities of each GPIO port are controlled by a set of seven registers. With these registers, it is possible to select the source of the interrupt, its polarity, and the edge properties. When one or more GPIO inputs cause an interrupt, a single interrupt output is sent to the interrupt controller for the entire GPIO port. For edge-triggered interrupts, software must clear the interrupt to enable any further interrupts. For a level-sensitive interrupt, it is assumed that the external source holds the level constant for the interrupt to be recognized by the controller.

Three registers are required to define the edge or sense that causes interrupts:

■ GPIO Interrupt Sense (GPIOIS) register (see page 265)

- GPIO Interrupt Both Edges (GPIOIBE) register (see page 266)
- GPIO Interrupt Event (GPIOIEV) register (see page 267)

Interrupts are enabled/disabled via the GPIO Interrupt Mask (GPIOIM) register (see page 268).

When an interrupt condition occurs, the state of the interrupt signal can be viewed in two locations: the **GPIO Raw Interrupt Status (GPIORIS)** and **GPIO Masked Interrupt Status (GPIOMIS)** registers (see page 269 and page 270). As the name implies, the **GPIOMIS** register only shows interrupt conditions that are allowed to be passed to the controller. The **GPIORIS** register indicates that a GPIO pin meets the conditions for an interrupt, but has not necessarily been sent to the controller.

In addition to providing GPIO functionality, PB4 can also be used as an external trigger for the ADC. If PB4 is configured as a non-masked interrupt pin (the appropriate bit of GPIOIM is set to 1), not only is an interrupt for PortB generated, but an external trigger signal is sent to the ADC. If the ADC Event Multiplexer Select (ADCEMUX) register is configured to use the external trigger, an ADC conversion is initiated.

If no other PortB pins are being used to generate interrupts, the **Interrupt 0-31 Set Enable (EN0)** register can disable the PortB interrupts, and the ADC interrupt can be used to read back the converted data. Otherwise, the PortB interrupt handler needs to ignore and clear interrupts on PB4, and wait for the ADC interrupt or the ADC interrupt must be disabled in the **EN0** register and the PortB interrupt handler must poll the ADC registers until the conversion is completed. See page 101 for more information.

Interrupts are cleared by writing a 1 to the appropriate bit of the **GPIO Interrupt Clear (GPIOICR)** register (see page 271).

When programming the following interrupt control registers, the interrupts should be masked (**GPIOIM** set to 0). Writing any value to an interrupt control register (**GPIOIS**, **GPIOIBE**, or **GPIOIEV**) can generate a spurious interrupt if the corresponding bits are enabled.

### 7.2.3 Mode Control

The GPIO pins can be controlled by either hardware or software. When hardware control is enabled via the **GPIO Alternate Function Select (GPIOAFSEL)** register (see page 272), the pin state is controlled by its alternate function (that is, the peripheral). Software control corresponds to GPIO mode, where the **GPIODATA** register is used to read/write the corresponding pins.

### 7.2.4 Commit Control

The GPIO commit control registers provide a layer of protection against accidental programming of critical hardware peripherals. Protection is currently provided for the five JTAG/SWD pins (PB7 and PC[3:0]). Writes to protected bits of the **GPIO Alternate Function Select (GPIOAFSEL)** register (see page 272) are not committed to storage unless the **GPIO Lock (GPIOLOCK)** register (see page 282) has been unlocked and the appropriate bits of the **GPIO Commit (GPIOCR)** register (see page 283) have been set to 1.

# 7.2.5 Pad Control

The pad control registers allow for GPIO pad configuration by software based on the application requirements. The pad control registers include the **GPIODR2R**, **GPIODR4R**, **GPIODR8R**, **GPIODDR**, **GPIOPDR**, **GPIOPDR**, **GPIOPDR**, and **GPIODEN** registers. These registers control drive strength, open-drain configuration, pull-up and pull-down resistors, slew-rate control and digital enable.

For special high-current applications, the GPIO output buffers may be used with the following restrictions. With the GPIO pins configured as 8-mA output drivers, a total of four GPIO outputs may

be used to sink current loads up to 18 mA each. At 18-mA sink current loading, the  $V_{OL}$  value is specified as 1.2 V. The high-current GPIO package pins must be selected such that there are only a maximum of two per side of the physical package or BGA pin group with the total number of high-current GPIO outputs not exceeding four for the entire package.

### 7.2.6 Identification

The identification registers configured at reset allow software to detect and identify the module as a GPIO block. The identification registers include the **GPIOPeriphID0-GPIOPeriphID7** registers as well as the **GPIOPCeIIID0-GPIOPCeIIID3** registers.

# 7.3 Initialization and Configuration

To use the GPIO, the peripheral clock must be enabled by setting the appropriate GPIO Port bit field (GPIOn) in the **RCGC2** register.

On reset, all GPIO pins (except for the five JTAG pins) are configured out of reset to be undriven (tristate): **GPIOAFSEL**=0, **GPIODEN**=0, **GPIOPDR**=0, and **GPIOPUR**=0. Table 7-6 on page 259 shows all possible configurations of the GPIO pads and the control register settings required to achieve them. Table 7-7 on page 259 shows how a rising edge interrupt would be configured for pin 2 of a GPIO port.

**Table 7-6. GPIO Pad Configuration Examples** 

Configuration	GPIO Reg	gister Bit Va	alue <sup>a</sup>							
Configuration	AFSEL	DIR	ODR	DEN	PUR	PDR	DR2R	DR4R	DR8R	SLR
Digital Input (GPIO)	0	0	0	1	?	?	Х	Х	Х	Х
Digital Output (GPIO)	0	1	0	1	?	?	?	?	?	?
Open Drain Output (GPIO)	0	1	1	1	Х	Х	?	?	?	?
Digital Input (Timer CCP)	1	Х	0	1	?	?	Х	Х	Х	Х
Digital Output (Timer PWM)	1	Х	0	1	?	?	?	?	?	?
Digital Input/Output (SSI)	1	Х	0	1	?	?	?	?	?	?
Digital Input/Output (UART)	1	Х	0	1	?	?	?	?	?	?
Analog Input (Comparator)	0	0	0	0	0	0	Х	Х	Х	Х
Digital Output (Comparator)	1	Х	0	1	?	?	?	?	?	?

a. X=Ignored (don't care bit)

**Table 7-7. GPIO Interrupt Configuration Example** 

		Pin 2 Bit Val	ue <sup>a</sup>						
Redister	Interrupt Event Trigger	7	6	5	4	3	2	1	0
GPIOIS	0=edge 1=level	Х	Х	Х	Х	Х	0	Х	Х

<sup>?=</sup>Can be either 0 or 1, depending on the configuration

**Table 7-7. GPIO Interrupt Configuration Example (continued)** 

	Desired	Pin 2 Bit Va	lue <sup>a</sup>	<sup>a</sup>						
Register	Register Interrupt Event Trigger	7	6	5	4	3	2	1	0	
GPIOIBE	0=single edge 1=both edges	Х	Х	Х	Х	Х	0	Х	Х	
GPIOIEV	0=Low level, or negative edge 1=High level, or positive edge		X	Х	Х	Х	1	Х	Х	
GPIOIM	0=masked 1=not masked	0	0	0	0	0	1	0	0	

a. X=Ignored (don't care bit)

# 7.4 Register Map

Table 7-8 on page 261 lists the GPIO registers. The offset listed is a hexadecimal increment to the register's address, relative to that GPIO port's base address:

■ GPIO Port A: 0x4000.4000

■ GPIO Port B: 0x4000.5000

■ GPIO Port C: 0x4000.6000

■ GPIO Port D: 0x4000.7000

GPIO Port E: 0x4002.4000

■ GPIO Port F: 0x4002.5000

■ GPIO Port G: 0x4002.6000

Note that the GPIO module clock must be enabled before the registers can be programmed (see page 216). There must be a delay of 3 system clocks after the GPIO module clock is enabled before any GPIO module registers are accessed.

**Important:** The GPIO registers in this chapter are duplicated in each GPIO block; however, depending on the block, all eight bits may not be connected to a GPIO pad. In those cases, writing to those unconnected bits has no effect, and reading those unconnected bits returns no meaningful data.

Note: The default reset value for the GPIOAFSEL, GPIOPUR, and GPIODEN registers are 0x0000.0000 for all GPIO pins, with the exception of the five JTAG/SWD pins (PB7 and PC[3:0]). These five pins default to JTAG/SWD functionality. Because of this, the default reset value of these registers for GPIO Port B is 0x0000.0080 while the default reset value for Port C is 0x0000.000F.

The default register type for the **GPIOCR** register is RO for all GPIO pins with the exception of the five JTAG/SWD pins (PB7 and PC[3:0]). These five pins are currently the only GPIOs that are protected by the **GPIOCR** register. Because of this, the register type for GPIO Port B7 and GPIO Port C[3:0] is R/W.

The default reset value for the **GPIOCR** register is 0x0000.00FF for all GPIO pins, with the exception of the five JTAG/SWD pins (PB7 and PC[3:0]). To ensure that the JTAG port is not accidentally programmed as a GPIO, these five pins default to non-committable. Because of this, the default reset value of **GPIOCR** for GPIO Port B is 0x0000.007F while the default reset value of GPIOCR for Port C is 0x0000.00F0.

Table 7-8. GPIO Register Map

Offset	Name	Type	Reset	Description	See page
0x000	GPIODATA	R/W	0x0000.0000	GPIO Data	263
0x400	GPIODIR	R/W	0x0000.0000	GPIO Direction	264
0x404	GPIOIS	R/W	0x0000.0000	GPIO Interrupt Sense	265
0x408	GPIOIBE	R/W	0x0000.0000	GPIO Interrupt Both Edges	266
0x40C	GPIOIEV	R/W	0x0000.0000	GPIO Interrupt Event	267
0x410	GPIOIM	R/W	0x0000.0000	GPIO Interrupt Mask	268
0x414	GPIORIS	RO	0x0000.0000	GPIO Raw Interrupt Status	269
0x418	GPIOMIS	RO	0x0000.0000	GPIO Masked Interrupt Status	270
0x41C	GPIOICR	W1C	0x0000.0000	GPIO Interrupt Clear	271
0x420	GPIOAFSEL	R/W	-	GPIO Alternate Function Select	272
0x500	GPIODR2R	R/W	0x0000.00FF	GPIO 2-mA Drive Select	274
0x504	GPIODR4R	R/W	0x0000.0000	GPIO 4-mA Drive Select	275
0x508	GPIODR8R	R/W	0x0000.0000	GPIO 8-mA Drive Select	276
0x50C	GPIOODR	R/W	0x0000.0000	GPIO Open Drain Select	277
0x510	GPIOPUR	R/W	-	GPIO Pull-Up Select	278
0x514	GPIOPDR	R/W	0x0000.0000	GPIO Pull-Down Select	279
0x518	GPIOSLR	R/W	0x0000.0000	GPIO Slew Rate Control Select	280
0x51C	GPIODEN	R/W	-	GPIO Digital Enable	281
0x520	GPIOLOCK	R/W	0x0000.0001	GPIO Lock	282
0x524	GPIOCR	-	-	GPIO Commit	283
0xFD0	GPIOPeriphID4	RO	0x0000.0000	GPIO Peripheral Identification 4	285
0xFD4	GPIOPeriphID5	RO	0x0000.0000	GPIO Peripheral Identification 5	286
0xFD8	GPIOPeriphID6	RO	0x0000.0000	GPIO Peripheral Identification 6	287
0xFDC	GPIOPeriphID7	RO	0x0000.0000	GPIO Peripheral Identification 7	288
0xFE0	GPIOPeriphID0	RO	0x0000.0061	GPIO Peripheral Identification 0	289
0xFE4	GPIOPeriphID1	RO	0x0000.0000	GPIO Peripheral Identification 1	290
0xFE8	GPIOPeriphID2	RO	0x0000.0018	GPIO Peripheral Identification 2	291
0xFEC	GPIOPeriphID3	RO	0x0000.0001	GPIO Peripheral Identification 3	292

Table 7-8. GPIO Register Map (continued)

Offset	Name	Туре	Reset	Description	See page
0xFF0	GPIOPCellID0	RO	0x0000.000D	GPIO PrimeCell Identification 0	293
0xFF4	GPIOPCellID1	RO	0x0000.00F0	GPIO PrimeCell Identification 1	294
0xFF8	GPIOPCellID2	RO	0x0000.0005	GPIO PrimeCell Identification 2	295
0xFFC	GPIOPCellID3	RO	0x0000.00B1	GPIO PrimeCell Identification 3	296

# 7.5 Register Descriptions

The remainder of this section lists and describes the GPIO registers, in numerical order by address offset.

# Register 1: GPIO Data (GPIODATA), offset 0x000

The **GPIODATA** register is the data register. In software control mode, values written in the **GPIODATA** register are transferred onto the GPIO port pins if the respective pins have been configured as outputs through the **GPIO Direction (GPIODIR)** register (see page 264).

In order to write to **GPIODATA**, the corresponding bits in the mask, resulting from the address bus bits [9:2], must be High. Otherwise, the bit values remain unchanged by the write.


Similarly, the values read from this register are determined for each bit by the mask bit derived from the address used to access the data register, bits [9:2]. Bits that are 1 in the address mask cause the corresponding bits in **GPIODATA** to be read, and bits that are 0 in the address mask cause the corresponding bits in **GPIODATA** to be read as 0, regardless of their value.

A read from **GPIODATA** returns the last bit value written if the respective pins are configured as outputs, or it returns the value on the corresponding input pin when these are configured as inputs. All bits are cleared by a reset.

#### GPIO Data (GPIODATA)

GPIO Port A base: 0x4000.4000 GPIO Port B base: 0x4000.5000 GPIO Port C base: 0x4000.6000 GPIO Port D base: 0x4000.7000 GPIO Port E base: 0x4002.4000 GPIO Port F base: 0x4002.5000 GPIO Port G base: 0x4002.6000 GPIO Port G base: 0x4002.6000

Type R/W, reset 0x0000.0000



Bit/Field	Name	Туре	Reset	Description
31:8	reserved	RO	0x00	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
7:0	DATA	R/W	0x00	GPIO Data


This register is virtually mapped to 256 locations in the address space. To facilitate the reading and writing of data to these registers by independent drivers, the data read from and the data written to the registers are masked by the eight address lines  $\mathtt{ipaddr[9:2]}$ . Reads from this register return its current state. Writes to this register only affect bits that are not masked by  $\mathtt{ipaddr[9:2]}$  and are configured as outputs. See "Data Register Operation" on page 257 for examples of reads and writes.

# Register 2: GPIO Direction (GPIODIR), offset 0x400

The GPIODIR register is the data direction register. Bits set to 1 in the GPIODIR register configure the corresponding pin to be an output, while bits set to 0 configure the pins to be inputs. All bits are cleared by a reset, meaning all GPIO pins are inputs by default.

### GPIO Direction (GPIODIR)

GPIO Port A base: 0x4000.4000 GPIO Port B base: 0x4000.5000 GPIO Port C base: 0x4000.6000 GPIO Port D base: 0x4000.7000 GPIO Port E base: 0x4002.4000 GPIO Port F base: 0x4002.5000 GPIO Port G base: 0x4002.6000 Offset 0x400 Type R/W, reset 0x0000.0000



Bit/Field	Name	Type	Reset	Description
31:8	reserved	RO	0x00	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
7:0	DIR	R/W	0x00	GPIO Data Direction

The DIR values are defined as follows:

- Pins are inputs.
- Pins are outputs.


RO

# Register 3: GPIO Interrupt Sense (GPIOIS), offset 0x404

The **GPIOIS** register is the interrupt sense register. Bits set to 1 in **GPIOIS** configure the corresponding pins to detect levels, while bits set to 0 configure the pins to detect edges. All bits are cleared by a reset.

### GPIO Interrupt Sense (GPIOIS)

GPIO Port A base: 0x4000.4000 GPIO Port B base: 0x4000.5000 GPIO Port C base: 0x4000.6000 GPIO Port D base: 0x4000.7000 GPIO Port E base: 0x4002.4000 GPIO Port F base: 0x4002.5000 GPIO Port G base: 0x4002.6000 Offset 0x404 Type R/W, reset 0x0000.0000



	15	14	13	12	11	10	9	8	7	6	5	4	3	2	1	0
	reserved							1		Į:	S L	1	1	_		
Type	RO	RO	RO	RO	RO	RO	RO	RO	R/W	R/W	R/W	R/W	R/W	R/W	R/W	R/W
Reset	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0

Bit/Field	Name	Туре	Reset	Description
31:8	reserved	RO	0x00	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
7:0	IS	R/W	0x00	GPIO Interrupt Sense

The  ${\tt IS}$  values are defined as follows:

- 0 Edge on corresponding pin is detected (edge-sensitive).
- 1 Level on corresponding pin is detected (level-sensitive).

# Register 4: GPIO Interrupt Both Edges (GPIOIBE), offset 0x408


The **GPIOIBE** register is the interrupt both-edges register. When the corresponding bit in the **GPIO Interrupt Sense (GPIOIS)** register (see page 265) is set to detect edges, bits set to High in **GPIOIBE** configure the corresponding pin to detect both rising and falling edges, regardless of the corresponding bit in the **GPIO Interrupt Event (GPIOIEV)** register (see page 267). Clearing a bit configures the pin to be controlled by **GPIOIEV**. All bits are cleared by a reset.

### GPIO Interrupt Both Edges (GPIOIBE)

GPIO Port A base: 0x4000.4000 GPIO Port B base: 0x4000.5000 GPIO Port C base: 0x4000.6000 GPIO Port D base: 0x4000.7000 GPIO Port E base: 0x4002.4000 GPIO Port F base: 0x4002.5000 GPIO Port G base: 0x4002.6000

Offset 0x408

Type R/W, reset 0x0000.0000



Bit/Field	Name	Туре	Reset	Description
31:8	reserved	RO	0x00	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
7:0	IBE	R/W	0x00	GPIO Interrupt Both Edges

The IBE values are defined as follows:

### Value Description

- 0 Interrupt generation is controlled by the GPIO Interrupt Event (GPIOIEV) register (see page 267).
- 1 Both edges on the corresponding pin trigger an interrupt.

**Note:** Single edge is determined by the corresponding bit in **GPIOIEV**.

# Register 5: GPIO Interrupt Event (GPIOIEV), offset 0x40C


The **GPIOIEV** register is the interrupt event register. Bits set to High in **GPIOIEV** configure the corresponding pin to detect rising edges or high levels, depending on the corresponding bit value in the **GPIO Interrupt Sense (GPIOIS)** register (see page 265). Clearing a bit configures the pin to detect falling edges or low levels, depending on the corresponding bit value in **GPIOIS**. All bits are cleared by a reset.

#### GPIO Interrupt Event (GPIOIEV)

GPIO Port A base: 0x4000.4000 GPIO Port B base: 0x4000.5000 GPIO Port C base: 0x4000.6000 GPIO Port D base: 0x4000.7000 GPIO Port E base: 0x4002.4000 GPIO Port F base: 0x4002.5000 GPIO Port G base: 0x4002.6000

Offset 0x40C

Type R/W, reset 0x0000.0000



Bit/Field	Name	Type	Reset	Description
31:8	reserved	RO	0x00	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
7:0	IEV	R/W	0x00	GPIO Interrupt Event

The IEV values are defined as follows:


- Falling edge or Low levels on corresponding pins trigger interrupts.
- Rising edge or High levels on corresponding pins trigger interrupts.


# Register 6: GPIO Interrupt Mask (GPIOIM), offset 0x410

The **GPIOIM** register is the interrupt mask register. Bits set to High in **GPIOIM** allow the corresponding pins to trigger their individual interrupts and the combined **GPIOINTR** line. Clearing a bit disables interrupt triggering on that pin. All bits are cleared by a reset.

### GPIO Interrupt Mask (GPIOIM)

GPIO Port A base: 0x4000.4000 GPIO Port B base: 0x4000.5000 GPIO Port C base: 0x4000.6000 GPIO Port D base: 0x4000.7000 GPIO Port E base: 0x4002.4000 GPIO Port F base: 0x4002.5000 GPIO Port G base: 0x4002.6000





Bit/Field	Name	Type	Reset	Description
31:8	reserved	RO	0x00	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
7:0	IME	R/W	0x00	GPIO Interrupt Mask Enable

The  ${\tt IME}$  values are defined as follows:

- 0 Corresponding pin interrupt is masked.
- 1 Corresponding pin interrupt is not masked.


# Register 7: GPIO Raw Interrupt Status (GPIORIS), offset 0x414

The **GPIORIS** register is the raw interrupt status register. Bits read High in **GPIORIS** reflect the status of interrupt trigger conditions detected (raw, prior to masking), indicating that all the requirements have been met, before they are finally allowed to trigger by the **GPIO Interrupt Mask (GPIOIM)** register (see page 268). Bits read as zero indicate that corresponding input pins have not initiated an interrupt. All bits are cleared by a reset.

#### GPIO Raw Interrupt Status (GPIORIS)

GPIO Port A base: 0x4000.4000 GPIO Port B base: 0x4000.5000 GPIO Port C base: 0x4000.6000 GPIO Port D base: 0x4000.7000 GPIO Port E base: 0x4002.4000 GPIO Port F base: 0x4002.5000 GPIO Port G base: 0x4002.6000 Offset 0x414





Bit/Field	Name	Туре	Reset	Description
31:8	reserved	RO	0x00	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
7:0	RIS	RO	0x00	GPIO Interrupt Raw Status

Reflects the status of interrupt trigger condition detection on pins (raw, prior to masking).

The RIS values are defined as follows:

- 0 Corresponding pin interrupt requirements not met.
- 1 Corresponding pin interrupt has met requirements.

# Register 8: GPIO Masked Interrupt Status (GPIOMIS), offset 0x418

The **GPIOMIS** register is the masked interrupt status register. Bits read High in **GPIOMIS** reflect the status of input lines triggering an interrupt. Bits read as Low indicate that either no interrupt has been generated, or the interrupt is masked.

In addition to providing GPIO functionality, PB4 can also be used as an external trigger for the ADC. If PB4 is configured as a non-masked interrupt pin (the appropriate bit of GPIOIM is set to 1), not only is an interrupt for PortB generated, but an external trigger signal is sent to the ADC. If the **ADC Event Multiplexer Select (ADCEMUX)** register is configured to use the external trigger, an ADC conversion is initiated.

If no other PortB pins are being used to generate interrupts, the **Interrupt 0-31 Set Enable (EN0)** register can disable the PortB interrupts, and the ADC interrupt can be used to read back the converted data. Otherwise, the PortB interrupt handler needs to ignore and clear interrupts on PB4, and wait for the ADC interrupt or the ADC interrupt must be disabled in the **EN0** register and the PortB interrupt handler must poll the ADC registers until the conversion is completed. See page 101 for more information.


**GPIOMIS** is the state of the interrupt after masking.

#### GPIO Masked Interrupt Status (GPIOMIS)

GPIO Port A base: 0x4000.4000 GPIO Port B base: 0x4000.5000 GPIO Port C base: 0x4000.6000 GPIO Port D base: 0x4000.7000 GPIO Port E base: 0x4002.4000 GPIO Port F base: 0x4002.5000 GPIO Port G base: 0x4002.6000

Offset 0x418

Type RO, reset 0x0000.0000



Bit/Field	Name	Type	Reset	Description
31:8	reserved	RO	0x00	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
7:0	MIS	RO	0x00	GPIO Masked Interrupt Status

Masked value of interrupt due to corresponding pin.

The MIS values are defined as follows:

- 0 Corresponding GPIO line interrupt not active.
- 1 Corresponding GPIO line asserting interrupt.


# Register 9: GPIO Interrupt Clear (GPIOICR), offset 0x41C

The **GPIOICR** register is the interrupt clear register. Writing a 1 to a bit in this register clears the corresponding interrupt edge detection logic register. Writing a 0 has no effect.

### GPIO Interrupt Clear (GPIOICR)

GPIO Port A base: 0x4000.4000 GPIO Port B base: 0x4000.5000 GPIO Port C base: 0x4000.6000 GPIO Port D base: 0x4000.7000 GPIO Port E base: 0x4002.4000 GPIO Port F base: 0x4002.5000 GPIO Port G base: 0x4002.6000 Offset 0x41C

Type W1C, reset 0x0000.0000



Bit/Field	Name	туре	Reset	Description
31:8	reserved	RO	0x00	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
7:0	IC	W1C	0x00	GPIO Interrupt Clear

The  ${\tt IC}$  values are defined as follows:

- 0 Corresponding interrupt is unaffected.
- 1 Corresponding interrupt is cleared.

# Register 10: GPIO Alternate Function Select (GPIOAFSEL), offset 0x420

The **GPIOAFSEL** register is the mode control select register. Writing a 1 to any bit in this register selects the hardware control for the corresponding GPIO line. All bits are cleared by a reset, therefore no GPIO line is set to hardware control by default.

The GPIO commit control registers provide a layer of protection against accidental programming of critical hardware peripherals. Protection is currently provided for the five JTAG/SWD pins (PB7 and PC[3:0]). Writes to protected bits of the **GPIO Alternate Function Select (GPIOAFSEL)** register (see page 272) are not committed to storage unless the **GPIO Lock (GPIOLOCK)** register (see page 282) has been unlocked and the appropriate bits of the **GPIO Commit (GPIOCR)** register (see page 283) have been set to 1.

Important: All GPIO pins are tri-stated by default (GPIOAFSEL=0, GPIODEN=0, GPIOPDR=0, and GPIOPUR=0), with the exception of the five JTAG/SWD pins (PB7 and PC[3:0]). The JTAG/SWD pins default to their JTAG/SWD functionality (GPIOAFSEL=1, GPIODEN=1 and GPIOPUR=1). A Power-On-Reset (POR) or asserting RST puts both groups of pins back to their default state.


While debugging systems where PB7 is being used as a GPIO, care must be taken to ensure that a low value is not applied to the pin when the part is reset. Because PB7 reverts to the  $\overline{\texttt{TRST}}$  function after reset, a Low value on the pin causes the JTAG controller to be reset, resulting in a loss of JTAG communication.

Caution – It is possible to create a software sequence that prevents the debugger from connecting to the Stellaris® microcontroller. If the program code loaded into flash immediately changes the JTAG pins to their GPIO functionality, the debugger may not have enough time to connect and halt the controller before the JTAG pin functionality switches. This may lock the debugger out of the part. This can be avoided with a software routine that restores JTAG functionality based on an external or software trigger.

### GPIO Alternate Function Select (GPIOAFSEL)

GPIO Port A base: 0x4000.4000 GPIO Port B base: 0x4000.5000 GPIO Port C base: 0x4000.6000 GPIO Port D base: 0x4000.7000 GPIO Port E base: 0x4002.4000 GPIO Port F base: 0x4002.5000 GPIO Port G base: 0x4002.6000 Offset 0x420

Type R/W, reset -



Bit/Field	Name	Type	Reset	Description
7:0	AFSEL	R/W	-	GPIO Alternate Function Select
				The AFSEL values are defined as follows:

#### Value Description

- 0 Software control of corresponding GPIO line (GPIO mode).
- 1 Hardware control of corresponding GPIO line (alternate hardware function).

#### Note: The defa

The default reset value for the **GPIOAFSEL**, **GPIOPUR**, and **GPIODEN** registers are 0x0000.0000 for all GPIO pins, with the exception of the five JTAG/SWD pins (PB7 and PC[3:0]). These five pins default to JTAG/SWD functionality. Because of this, the default reset value of these registers for GPIO Port B is 0x0000.0080 while the default reset value for Port C is 0x0000.000F.

# Register 11: GPIO 2-mA Drive Select (GPIODR2R), offset 0x500

The GPIODR2R register is the 2-mA drive control register. It allows for each GPIO signal in the port to be individually configured without affecting the other pads. When writing a DRV2 bit for a GPIO signal, the corresponding DRV4 bit in the GPIODR4R register and the DRV8 bit in the GPIODR8R register are automatically cleared by hardware.

#### GPIO 2-mA Drive Select (GPIODR2R)

GPIO Port A base: 0x4000.4000 GPIO Port B base: 0x4000.5000 GPIO Port C base: 0x4000.6000 GPIO Port D base: 0x4000.7000 GPIO Port E base: 0x4002.4000 GPIO Port F base: 0x4002.5000 GPIO Port G base: 0x4002.6000 Offset 0x500

RO

0

Type

Reset

RO

0

RO

0

RO

0

RO


0

RO

0

RO

0



RO

0

R/W

R/W

Bit/Field	Name	туре	Reset	Description
31:8	reserved	RO	0x00	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
7:0	DRV2	R/W	0xFF	Output Pad 2-mA Drive Enable

A write of 1 to either GPIODR4[n] or GPIODR8[n] clears the corresponding 2-mA enable bit. The change is effective on the second clock cycle after the write.

R/W

R/W


1

# Register 12: GPIO 4-mA Drive Select (GPIODR4R), offset 0x504

The **GPIODR4R** register is the 4-mA drive control register. It allows for each GPIO signal in the port to be individually configured without affecting the other pads. When writing the DRV4 bit for a GPIO signal, the corresponding DRV2 bit in the **GPIODR2R** register and the DRV8 bit in the **GPIODR8R** register are automatically cleared by hardware.

### GPIO 4-mA Drive Select (GPIODR4R)

GPIO Port A base: 0x4000.4000 GPIO Port B base: 0x4000.5000 GPIO Port C base: 0x4000.6000 GPIO Port D base: 0x4000.7000 GPIO Port E base: 0x4002.4000 GPIO Port F base: 0x4002.5000 GPIO Port G base: 0x4002.6000 Offset 0x504 Type R/W, reset 0x0000.0000



Bit/Field	Name	Type	Reset	Description
31:8	reserved	RO	0x00	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
7:0	DRV4	R/W	0x00	Output Pad 4-mA Drive Enable

A write of 1 to either **GPIODR2[n]** or **GPIODR8[n]** clears the corresponding 4-mA enable bit. The change is effective on the second clock cycle after the write.


# Register 13: GPIO 8-mA Drive Select (GPIODR8R), offset 0x508

The **GPIODR8R** register is the 8-mA drive control register. It allows for each GPIO signal in the port to be individually configured without affecting the other pads. When writing the DRV8 bit for a GPIO signal, the corresponding DRV2 bit in the **GPIODR2R** register and the DRV4 bit in the **GPIODR4R** register are automatically cleared by hardware.

#### GPIO 8-mA Drive Select (GPIODR8R)

GPIO Port A base: 0x4000.4000 GPIO Port B base: 0x4000.5000 GPIO Port C base: 0x4000.6000 GPIO Port D base: 0x4000.7000 GPIO Port E base: 0x4002.4000 GPIO Port F base: 0x4002.5000 GPIO Port G base: 0x4002.6000 Offset 0x508

Type R/W, reset 0x0000.0000



Bit/Field	Name	Type	Reset	Description
31:8	reserved	RO	0x00	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
7:0	DRV8	R/W	0x00	Output Pad 8-mA Drive Enable

A write of 1 to either **GPIODR2[n]** or **GPIODR4[n]** clears the corresponding 8-mA enable bit. The change is effective on the second clock cycle after the write.


# Register 14: GPIO Open Drain Select (GPIOODR), offset 0x50C

The **GPIOODR** register is the open drain control register. Setting a bit in this register enables the open drain configuration of the corresponding GPIO pad. When open drain mode is enabled, the corresponding bit should also be set in the **GPIO Digital Enable (GPIODEN)** register (see page 281). Corresponding bits in the drive strength registers (**GPIODR2R**, **GPIODR4R**, **GPIODR8R**, and **GPIOSLR**) can be set to achieve the desired rise and fall times. The GPIO acts as an open-drain input if the corresponding bit in the **GPIODIR** register is cleared. If open drain is selected while the GPIO is configured as an input, the GPIO will remain an input and the open-drain selection has no effect until the GPIO is changed to an output.

### GPIO Open Drain Select (GPIOODR)

GPIO Port A base: 0x4000.4000 GPIO Port B base: 0x4000.5000 GPIO Port C base: 0x4000.6000 GPIO Port D base: 0x4000.7000 GPIO Port E base: 0x4002.4000 GPIO Port F base: 0x4002.5000 GPIO Port G base: 0x4002.6000 Offset 0x50C

Type R/W, reset 0x0000.0000



Bit/Field	Name	Type	Reset	Description
31:8	reserved	RO	0x00	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
7:0	ODE	R/W	0x00	Output Pad Open Drain Enable
				The ODE values are defined as follows:


- 0 Open drain configuration is disabled.
- 1 Open drain configuration is enabled.

# Register 15: GPIO Pull-Up Select (GPIOPUR), offset 0x510

The **GPIOPUR** register is the pull-up control register. When a bit is set to 1, it enables a weak pull-up resistor on the corresponding GPIO signal. Setting a bit in **GPIOPUR** automatically clears the corresponding bit in the **GPIO Pull-Down Select (GPIOPDR)** register (see page 279).

### GPIO Pull-Up Select (GPIOPUR)

GPIO Port A base: 0x4000.4000 GPIO Port B base: 0x4000.5000 GPIO Port C base: 0x4000.6000 GPIO Port D base: 0x4000.7000 GPIO Port E base: 0x4002.4000 GPIO Port F base: 0x4002.5000 GPIO Port G base: 0x4002.6000 GPIO Port G base: 0x4002.6000 Offset 0x510 Type R/W, reset -



Bit/Field	Name	Type	Reset	Description
31:8	reserved	RO	0x00	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
7:0	PUF	R/W	_	Pad Weak Pull-Up Enable

rad Weak Full-Op Lilable

A write of 1 to **GPIOPDR[n]** clears the corresponding **GPIOPUR[n]** enables. The change is effective on the second clock cycle after the write.

Note:


The default reset value for the **GPIOAFSEL**, **GPIOPUR**, and **GPIODEN** registers are 0x0000.0000 for all GPIO pins, with the exception of the five JTAG/SWD pins (PB7 and PC[3:0]). These five pins default to JTAG/SWD functionality. Because of this, the default reset value of these registers for GPIO Port B is 0x0000.0080 while the default reset value for Port C is 0x0000.000F.

# Register 16: GPIO Pull-Down Select (GPIOPDR), offset 0x514

The **GPIOPDR** register is the pull-down control register. When a bit is set to 1, it enables a weak pull-down resistor on the corresponding GPIO signal. Setting a bit in **GPIOPDR** automatically clears the corresponding bit in the **GPIO Pull-Up Select (GPIOPUR)** register (see page 278).

### GPIO Pull-Down Select (GPIOPDR)

GPIO Port A base: 0x4000.4000 GPIO Port B base: 0x4000.5000 GPIO Port C base: 0x4000.6000 GPIO Port D base: 0x4000.7000 GPIO Port E base: 0x4002.4000 GPIO Port F base: 0x4002.5000 GPIO Port G base: 0x4002.6000 Offset 0x514 Type R/W, reset 0x0000.0000



Bit/Field	Name	Type	Reset	Description
31:8	reserved	RO	0x00	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
7:0	PDE	R/W	0x00	Pad Weak Pull-Down Enable


A write of 1 to **GPIOPUR[n]** clears the corresponding **GPIOPDR[n]** enables. The change is effective on the second clock cycle after the write.

# Register 17: GPIO Slew Rate Control Select (GPIOSLR), offset 0x518

The GPIOSLR register is the slew rate control register. Slew rate control is only available when using the 8-mA drive strength option via the GPIO 8-mA Drive Select (GPIODR8R) register (see page 276).

### GPIO Slew Rate Control Select (GPIOSLR)

GPIO Port A base: 0x4000.4000 GPIO Port B base: 0x4000.5000 GPIO Port C base: 0x4000.6000 GPIO Port D base: 0x4000.7000 GPIO Port E base: 0x4002.4000 GPIO Port F base: 0x4002.5000 GPIO Port G base: 0x4002.6000 Offset 0x518 Type R/W, reset 0x0000.0000



Bit/Field	Name	Туре	Reset	Description
31:8	reserved	RO	0x00	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
7:0	SRL	R/W	0x00	Slew Rate Limit Enable (8-mA drive only)

The SRL values are defined as follows:

- Slew rate control disabled.
- Slew rate control enabled.


# Register 18: GPIO Digital Enable (GPIODEN), offset 0x51C

**Note:** Pins configured as digital inputs are Schmitt-triggered.

The **GPIODEN** register is the digital enable register. By default, with the exception of the GPIO signals used for JTAG/SWD function, all other GPIO signals are configured out of reset to be undriven (tristate). Their digital function is disabled; they do not drive a logic value on the pin and they do not allow the pin voltage into the GPIO receiver. To use the pin in a digital function (either GPIO or alternate function), the corresponding GPIODEN bit must be set.

#### GPIO Digital Enable (GPIODEN)

GPIO Port A base: 0x4000.4000 GPIO Port B base: 0x4000.5000 GPIO Port C base: 0x4000.6000 GPIO Port D base: 0x4000.7000 GPIO Port E base: 0x4002.4000 GPIO Port F base: 0x4002.5000 GPIO Port G base: 0x4002.6000 Offset 0x51C Type R/W, reset -



Bit/Field	Name	Туре	Reset	Description
31:8	reserved	RO	0x00	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
7:0	DEN	R/W	-	Digital Enable

The DEN values are defined as follows:

#### Value Description

- 0 Digital functions disabled.
- Digital functions enabled.

Note: The default reset value for the GPIOAFSEL,
GPIOPUR, and GPIODEN registers are 0x0000.0000
for all GPIO pins, with the exception of the five
JTAG/SWD pins (PB7 and PC[3:0]). These five pins
default to JTAG/SWD functionality. Because of this,
the default reset value of these registers for GPIO
Port B is 0x0000.0080 while the default reset value

for Port C is 0x0000.000F.


# Register 19: GPIO Lock (GPIOLOCK), offset 0x520

The **GPIOLOCK** register enables write access to the **GPIOCR** register (see page 283). Writing 0x1ACC.E551 to the **GPIOLOCK** register will unlock the **GPIOCR** register. Writing any other value to the **GPIOLOCK** register re-enables the locked state. Reading the **GPIOLOCK** register returns the lock status rather than the 32-bit value that was previously written. Therefore, when write accesses are disabled, or locked, reading the **GPIOLOCK** register returns 0x00000001. When write accesses are enabled, or unlocked, reading the **GPIOLOCK** register returns 0x000000000.

#### GPIO Lock (GPIOLOCK)

GPIO Port A base: 0x4000.4000 GPIO Port B base: 0x4000.5000 GPIO Port C base: 0x4000.6000 GPIO Port D base: 0x4000.7000 GPIO Port E base: 0x4002.4000 GPIO Port F base: 0x4002.5000 GPIO Port G base: 0x4002.6000 Offset 0x520

Type R/W, reset 0x0000.0001



Bit/Field	Name	Type	Reset	Description
31:0	LOCK	R/W	0x0000.0001	GPIO Lock

A write of the value 0x1ACC.E551 unlocks the **GPIO Commit (GPIOCR)** register for write access.

A write of any other value or a write to the **GPIOCR** register reapplies the lock, preventing any register updates. A read of this register returns the following values:

Value Description
0x0000.0001 Locked
0x0000.0000 Unlocked

### Register 20: GPIO Commit (GPIOCR), offset 0x524

The GPIOCR register is the commit register. The value of the GPIOCR register determines which bits of the GPIOAFSEL register are committed when a write to the GPIOAFSEL register is performed. If a bit in the GPIOCR register is a zero, the data being written to the corresponding bit in the GPIOAFSEL register will not be committed and will retain its previous value. If a bit in the GPIOCR register is a one, the data being written to the corresponding bit of the GPIOAFSEL register will be committed to the register and will reflect the new value.

The contents of the GPIOCR register can only be modified if the GPIOLOCK register is unlocked. Writes to the GPIOCR register are ignored if the GPIOLOCK register is locked.

Important: This register is designed to prevent accidental programming of the registers that control connectivity to the JTAG/SWD debug hardware. By initializing the bits of the GPIOCR register to 0 for PB7 and PC[3:0], the JTAG/SWD debug port can only be converted to GPIOs through a deliberate set of writes to the GPIOLOCK, GPIOCR, and the corresponding registers.


> Because this protection is currently only implemented on the JTAG/SWD pins on PB7 and PC[3:0], all of the other bits in the **GPIOCR** registers cannot be written with 0x0. These bits are hardwired to 0x1, ensuring that it is always possible to commit new values to the **GPIOAFSEL**register bits of these other pins.

#### GPIO Commit (GPIOCR)

GPIO Port A base: 0x4000.4000 GPIO Port B base: 0x4000 5000 GPIO Port C base: 0x4000.6000 GPIO Port D base: 0x4000.7000 GPIO Port E base: 0x4002.4000 GPIO Port F base: 0x4002.5000

GPIO Port G base: 0x4002.6000 Offset 0x524

Type -, reset -



Description

Bit/Field Name Type Reset 31:8 reserved RO 0x00

Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.

Bit/Field	Name	Type	Reset	Description
7:0	CR	_	_	GPIO Commit

On a bit-wise basis, any bit set allows the corresponding **GPIOAFSEL** bit to be set to its alternate function.

#### Note:

The default register type for the **GPIOCR** register is RO for all GPIO pins with the exception of the five JTAG/SWD pins (PB7 and PC[3:0]). These five pins are currently the only GPIOs that are protected by the **GPIOCR** register. Because of this, the register type for GPIO Port B7 and GPIO Port C[3:0] is R/W.


The default reset value for the **GPIOCR** register is 0x0000.00FF for all GPIO pins, with the exception of the five JTAG/SWD pins (PB7 and PC[3:0]). To ensure that the JTAG port is not accidentally programmed as a GPIO, these five pins default to non-committable. Because of this, the default reset value of **GPIOCR** for GPIO Port B is 0x0000.007F while the default reset value of GPIOCR for Port C is 0x0000.00F0.

# Register 21: GPIO Peripheral Identification 4 (GPIOPeriphID4), offset 0xFD0

The GPIOPeriphID4, GPIOPeriphID5, GPIOPeriphID6, and GPIOPeriphID7 registers can conceptually be treated as one 32-bit register; each register contains eight bits of the 32-bit register, used by software to identify the peripheral.

### GPIO Peripheral Identification 4 (GPIOPeriphID4)

GPIO Port A base: 0x4000.4000 GPIO Port B base: 0x4000.5000 GPIO Port C base: 0x4000.6000 GPIO Port D base: 0x4000.7000 GPIO Port E base: 0x4002.4000 GPIO Port F base: 0x4002.5000 GPIO Port G base: 0x4002.6000 Offset 0xFD0 Type RO, reset 0x0000.0000




Bit/Field	Name	Type	Reset	Description
31:8	reserved	RO	0x00	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
7:0	PID4	RO	0x00	GPIO Peripheral ID Register[7:0]


# Register 22: GPIO Peripheral Identification 5 (GPIOPeriphID5), offset 0xFD4

The **GPIOPeriphID4**, **GPIOPeriphID5**, **GPIOPeriphID6**, and **GPIOPeriphID7** registers can conceptually be treated as one 32-bit register; each register contains eight bits of the 32-bit register, used by software to identify the peripheral.

### GPIO Peripheral Identification 5 (GPIOPeriphID5)

GPIO Port A base: 0x4000.4000 GPIO Port B base: 0x4000.5000 GPIO Port C base: 0x4000.6000 GPIO Port D base: 0x4000.7000 GPIO Port E base: 0x4002.4000 GPIO Port F base: 0x4002.5000 GPIO Port G base: 0x4002.6000






Bit/Field	Name	Type	Reset	Description
31:8	reserved	RO	0x00	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
7:0	PID5	RO	0x00	GPIO Peripheral ID Register[15:8]

# Register 23: GPIO Peripheral Identification 6 (GPIOPeriphID6), offset 0xFD8

The GPIOPeriphID4, GPIOPeriphID5, GPIOPeriphID6, and GPIOPeriphID7 registers can conceptually be treated as one 32-bit register; each register contains eight bits of the 32-bit register, used by software to identify the peripheral.

### GPIO Peripheral Identification 6 (GPIOPeriphID6)

GPIO Port A base: 0x4000.4000 GPIO Port B base: 0x4000.5000 GPIO Port C base: 0x4000.6000 GPIO Port D base: 0x4000.7000 GPIO Port E base: 0x4002.4000 GPIO Port F base: 0x4002.5000 GPIO Port G base: 0x4002.6000 Offset 0xFD8
Type RO, reset 0x0000.0000



Bit/Field	Name	Type	Reset	Description
31:8	reserved	RO	0x00	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
7:0	PID6	RO	0x00	GPIO Peripheral ID Register[23:16]


# Register 24: GPIO Peripheral Identification 7 (GPIOPeriphID7), offset 0xFDC

The GPIOPeriphID4, GPIOPeriphID5, GPIOPeriphID6, and GPIOPeriphID7 registers can conceptually be treated as one 32-bit register; each register contains eight bits of the 32-bit register, used by software to identify the peripheral.

### GPIO Peripheral Identification 7 (GPIOPeriphID7)

GPIO Port A base: 0x4000.4000 GPIO Port B base: 0x4000.5000 GPIO Port C base: 0x4000.6000 GPIO Port D base: 0x4000.7000 GPIO Port E base: 0x4002.4000 GPIO Port F base: 0x4002.5000 GPIO Port G base: 0x4002.6000

Offset 0xFDC Type RO, reset 0x0000.0000




Bit/Field	Name	Type	Reset	Description
31:8	reserved	RO	0x00	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
7:0	PID7	RO	0x00	GPIO Peripheral ID Register[31:24]

# Register 25: GPIO Peripheral Identification 0 (GPIOPeriphID0), offset 0xFE0

The GPIOPeriphID0, GPIOPeriphID1, GPIOPeriphID2, and GPIOPeriphID3 registers can conceptually be treated as one 32-bit register; each register contains eight bits of the 32-bit register, used by software to identify the peripheral.

### GPIO Peripheral Identification 0 (GPIOPeriphID0)

GPIO Port A base: 0x4000.4000 GPIO Port B base: 0x4000.5000 GPIO Port C base: 0x4000.6000 GPIO Port D base: 0x4000.7000 GPIO Port E base: 0x4002.4000 GPIO Port F base: 0x4002.5000 GPIO Port G base: 0x4002.6000 Offset 0xFE0
Type RO, reset 0x0000.0061



Bit/Field	Name	Type	Reset	Description
31:8	reserved	RO	0x00	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
7:0	PID0	RO	0x61	GPIO Peripheral ID Register[7:0]
				Can be used by software to identify the presence of this peripheral.


# Register 26: GPIO Peripheral Identification 1 (GPIOPeriphID1), offset 0xFE4

The **GPIOPeriphID0**, **GPIOPeriphID1**, **GPIOPeriphID2**, and **GPIOPeriphID3** registers can conceptually be treated as one 32-bit register; each register contains eight bits of the 32-bit register, used by software to identify the peripheral.

### GPIO Peripheral Identification 1 (GPIOPeriphID1)

GPIO Port A base: 0x4000.4000 GPIO Port B base: 0x4000.5000 GPIO Port C base: 0x4000.6000 GPIO Port D base: 0x4000.7000 GPIO Port E base: 0x4002.4000 GPIO Port F base: 0x4002.5000 GPIO Port G base: 0x4002.6000 Offset 0xFE4

Offset 0xFE4
Type RO, reset 0x0000.0000



Bit/Field	Name	Type	Reset	Description
31:8	reserved	RO	0x00	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
7:0	PID1	RO	0x00	GPIO Peripheral ID Register[15:8]

Can be used by software to identify the presence of this peripheral.


# Register 27: GPIO Peripheral Identification 2 (GPIOPeriphID2), offset 0xFE8

The **GPIOPeriphID0**, **GPIOPeriphID1**, **GPIOPeriphID2**, and **GPIOPeriphID3** registers can conceptually be treated as one 32-bit register; each register contains eight bits of the 32-bit register, used by software to identify the peripheral.

### GPIO Peripheral Identification 2 (GPIOPeriphID2)

GPIO Port A base: 0x4000.4000 GPIO Port B base: 0x4000.5000 GPIO Port C base: 0x4000.6000 GPIO Port D base: 0x4000.7000 GPIO Port E base: 0x4002.4000 GPIO Port F base: 0x4002.5000 GPIO Port G base: 0x4002.6000 Offset 0xFER

Offset 0xFE8
Type RO, reset 0x0000.0018



Bit/Field	Name	Type	Reset	Description
31:8	reserved	RO	0x00	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
7:0	PID2	RO	0x18	GPIO Peripheral ID Register[23:16]

Can be used by software to identify the presence of this peripheral.


# Register 28: GPIO Peripheral Identification 3 (GPIOPeriphID3), offset 0xFEC

The **GPIOPeriphID0**, **GPIOPeriphID1**, **GPIOPeriphID2**, and **GPIOPeriphID3** registers can conceptually be treated as one 32-bit register; each register contains eight bits of the 32-bit register, used by software to identify the peripheral.

### GPIO Peripheral Identification 3 (GPIOPeriphID3)

GPIO Port A base: 0x4000.4000 GPIO Port B base: 0x4000.5000 GPIO Port C base: 0x4000.6000 GPIO Port D base: 0x4000.7000 GPIO Port E base: 0x4002.4000 GPIO Port F base: 0x4002.5000 GPIO Port G base: 0x4002.6000

Offset 0xFEC
Type RO, reset 0x0000.0001



Bit/Field	Name	Type	Reset	Description
31:8	reserved	RO	0x00	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
7:0	PID3	RO	0x01	GPIO Peripheral ID Register[31:24]


Can be used by software to identify the presence of this peripheral.

# Register 29: GPIO PrimeCell Identification 0 (GPIOPCellID0), offset 0xFF0

The **GPIOPCeIIID1**, **GPIOPCeIIID1**, and **GPIOPCeIIID3** registers are four 8-bit wide registers, that can conceptually be treated as one 32-bit register. The register is used as a standard cross-peripheral identification system.

### GPIO PrimeCell Identification 0 (GPIOPCellID0)

GPIO Port A base: 0x4000.4000 GPIO Port B base: 0x4000.5000 GPIO Port C base: 0x4000.6000 GPIO Port D base: 0x4000.7000 GPIO Port E base: 0x4002.4000 GPIO Port F base: 0x4002.5000 GPIO Port G base: 0x4002.6000 GPIO Port G base: 0x4002.6000 Offset 0xFF0 Type RO, reset 0x0000.000D



Bit/Field	Name	Type	Reset	Description
31:8	reserved	RO	0x00	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
7:0	CID0	RO	0x0D	GPIO PrimeCell ID Register[7:0]


# Register 30: GPIO PrimeCell Identification 1 (GPIOPCellID1), offset 0xFF4

The **GPIOPCeIIID1**, **GPIOPCeIIID1**, and **GPIOPCeIIID3** registers are four 8-bit wide registers, that can conceptually be treated as one 32-bit register. The register is used as a standard cross-peripheral identification system.

### GPIO PrimeCell Identification 1 (GPIOPCellID1)

GPIO Port A base: 0x4000.4000 GPIO Port B base: 0x4000.5000 GPIO Port C base: 0x4000.6000 GPIO Port D base: 0x4000.7000 GPIO Port E base: 0x4002.4000 GPIO Port F base: 0x4002.5000 GPIO Port G base: 0x4002.6000 Offset 0x

Offset 0xFF4
Type RO, reset 0x0000.00F0



Bit/Field	Name	Type	Reset	Description
31:8	reserved	RO	0x00	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
7:0	CID1	RO	0xF0	GPIO PrimeCell ID Register[15:8]


### Register 31: GPIO PrimeCell Identification 2 (GPIOPCellID2), offset 0xFF8

The GPIOPCellID0, GPIOPCellID1, GPIOPCellID2, and GPIOPCellID3 registers are four 8-bit wide registers, that can conceptually be treated as one 32-bit register. The register is used as a standard cross-peripheral identification system.

### GPIO PrimeCell Identification 2 (GPIOPCellID2)

GPIO Port A base: 0x4000.4000 GPIO Port B base: 0x4000.5000 GPIO Port C base: 0x4000.6000 GPIO Port D base: 0x4000.7000 GPIO Port E base: 0x4002.4000 GPIO Port F base: 0x4002.5000 GPIO Port G base: 0x4002.6000 Offset 0xFF8
Type RO, reset 0x0000.0005






Bit/Field	Name	Type	Reset	Description
31:8	reserved	RO	0x00	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
7:0	CID2	RO	0x05	GPIO PrimeCell ID Register[23:16]


# Register 32: GPIO PrimeCell Identification 3 (GPIOPCellID3), offset 0xFFC

The **GPIOPCeIIID1**, **GPIOPCeIIID1**, and **GPIOPCeIIID3** registers are four 8-bit wide registers, that can conceptually be treated as one 32-bit register. The register is used as a standard cross-peripheral identification system.

### GPIO PrimeCell Identification 3 (GPIOPCellID3)

GPIO Port A base: 0x4000.4000 GPIO Port B base: 0x4000.5000 GPIO Port C base: 0x4000.6000 GPIO Port D base: 0x4000.7000 GPIO Port E base: 0x4002.4000 GPIO Port F base: 0x4002.5000 GPIO Port G base: 0x4002.6000 Offset 0x





Bit/Field	Name	Type	Reset	Description
31:8	reserved	RO	0x00	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
7:0	CID3	RO	0xB1	GPIO PrimeCell ID Register[31:24]

# 8 General-Purpose Timers

Programmable timers can be used to count or time external events that drive the Timer input pins. The Stellaris<sup>®</sup> General-Purpose Timer Module (GPTM) contains three GPTM blocks (Timer0, Timer1, and Timer 2). Each GPTM block provides two 16-bit timers/counters (referred to as TimerA and TimerB) that can be configured to operate independently as timers or event counters, or configured to operate as one 32-bit timer or one 32-bit Real-Time Clock (RTC).

In addition, timers can be used to trigger analog-to-digital conversions (ADC). The ADC trigger signals from all of the general-purpose timers are ORed together before reaching the ADC module, so only one timer should be used to trigger ADC events.

The GPT Module is one timing resource available on the Stellaris microcontrollers. Other timer resources include the System Timer (SysTick) (see 86).

The General-Purpose Timers provide the following features:

- Three General-Purpose Timer Modules (GPTM), each of which provides two 16-bit timers/counters. Each GPTM can be configured to operate independently:
  - As a single 32-bit timer
  - As one 32-bit Real-Time Clock (RTC) to event capture
  - For Pulse Width Modulation (PWM)
  - To trigger analog-to-digital conversions
- 32-bit Timer modes
  - Programmable one-shot timer
  - Programmable periodic timer
  - Real-Time Clock when using an external 32.768-KHz clock as the input
  - User-enabled stalling when the controller asserts CPU Halt flag during debug
  - ADC event trigger
- 16-bit Timer modes
  - General-purpose timer function with an 8-bit prescaler (for one-shot and periodic modes only)
  - Programmable one-shot timer
  - Programmable periodic timer
  - User-enabled stalling when the controller asserts CPU Halt flag during debug
  - ADC event trigger
- 16-bit Input Capture modes
  - Input edge count capture

- Input edge time capture
- 16-bit PWM mode
  - Simple PWM mode with software-programmable output inversion of the PWM signal

# 8.1 Block Diagram

**Note:** In Figure 8-1 on page 298, the specific CCP pins available depend on the Stellaris device. See Table 8-1 on page 298 for the available CCPs.

Figure 8-1. GPTM Module Block Diagram




Table 8-1. Available CCP Pins

Timer	16-Bit Up/Down Counter	Even CCP Pin	Odd CCP Pin
Timer 0	TimerA	CCP0	-
	TimerB	-	CCP1
Timer 1	TimerA	CCP2	-
	TimerB	-	CCP3
Timer 2	TimerA	-	-
	TimerB	-	-

# 8.2 Signal Description

Table 8-2 on page 299 and Table 8-3 on page 299 list the external signals of the GP Timer module and describe the function of each. The GP Timer signals are alternate functions for some GPIO signals and default to be GPIO signals at reset. The column in the table below titled "Pin Assignment"

lists the possible GPIO pin placements for these GP Timer signals. The AFSEL bit in the **GPIO Alternate Function Select (GPIOAFSEL)** register (page 272) should be set to choose the GP Timer function. For more information on configuring GPIOs, see "General-Purpose Input/Outputs (GPIOs)" on page 251.

Table 8-2. General-Purpose Timers Signals (100LQFP)

Pin Name	Pin Number	Pin Type	Buffer Type <sup>a</sup>	Description
CCP0	66	I/O	TTL	Capture/Compare/PWM 0.
CCP1	34	I/O	TTL	Capture/Compare/PWM 1.
CCP2	67	I/O	TTL	Capture/Compare/PWM 2.
CCP3	23	I/O	TTL	Capture/Compare/PWM 3.

a. The TTL designation indicates the pin has TTL-compatible voltage levels.

Table 8-3. General-Purpose Timers Signals (108BGA)

Pin Name	Pin Number	Pin Type	Buffer Type <sup>a</sup>	Description
CCP0	E12	I/O	TTL	Capture/Compare/PWM 0.
CCP1	L6	I/O	TTL	Capture/Compare/PWM 1.
CCP2	D12	I/O	TTL	Capture/Compare/PWM 2.
CCP3	M2	I/O	TTL	Capture/Compare/PWM 3.

a. The TTL designation indicates the pin has TTL-compatible voltage levels.

## 8.3 Functional Description

The main components of each GPTM block are two free-running 16-bit up/down counters (referred to as TimerA and TimerB), two 16-bit match registers, two prescaler match registers, and two 16-bit load/initialization registers and their associated control functions. The exact functionality of each GPTM is controlled by software and configured through the register interface.

Software configures the GPTM using the **GPTM Configuration (GPTMCFG)** register (see page 309), the **GPTM TimerA Mode (GPTMTAMR)** register (see page 310), and the **GPTM TimerB Mode (GPTMTBMR)** register (see page 312). When in one of the 32-bit modes, the timer can only act as a 32-bit timer. However, when configured in 16-bit mode, the GPTM can have its two 16-bit timers configured in any combination of the 16-bit modes.

### 8.3.1 GPTM Reset Conditions

After reset has been applied to the GPTM module, the module is in an inactive state, and all control registers are cleared and in their default states. Counters TimerA and TimerB are initialized to 0xFFFF, along with their corresponding load registers: the GPTM TimerA Interval Load (GPTMTBILR) register (see page 323) and the GPTM TimerB Interval Load (GPTMTBILR) register (see page 324). The prescale counters are initialized to 0x00: the GPTM TimerA Prescale (GPTMTAPR) register (see page 327) and the GPTM TimerB Prescale (GPTMTBPR) register (see page 328).

### 8.3.2 32-Bit Timer Operating Modes

This section describes the three GPTM 32-bit timer modes (One-Shot, Periodic, and RTC) and their configuration.

The GPTM is placed into 32-bit mode by writing a 0 (One-Shot/Periodic 32-bit timer mode) or a 1 (RTC mode) to the **GPTM Configuration (GPTMCFG)** register. In both configurations, certain GPTM registers are concatenated to form pseudo 32-bit registers. These registers include:

- GPTM TimerA Interval Load (GPTMTAILR) register [15:0], see page 323
- GPTM TimerB Interval Load (GPTMTBILR) register [15:0], see page 324
- **GPTM TimerA (GPTMTAR)** register [15:0], see page 331
- **GPTM TimerB (GPTMTBR)** register [15:0], see page 332

In the 32-bit modes, the GPTM translates a 32-bit write access to **GPTMTAILR** into a write access to both **GPTMTAILR** and **GPTMTBILR**. The resulting word ordering for such a write operation is:

```
GPTMTBILR[15:0]:GPTMTAILR[15:0]
```

Likewise, a read access to **GPTMTAR** returns the value:

```
GPTMTBR[15:0]:GPTMTAR[15:0]
```

#### 8.3.2.1 32-Bit One-Shot/Periodic Timer Mode

In 32-bit one-shot and periodic timer modes, the concatenated versions of the TimerA and TimerB registers are configured as a 32-bit down-counter. The selection of one-shot or periodic mode is determined by the value written to the TAMR field of the **GPTM TimerA Mode (GPTMTAMR)** register (see page 310), and there is no need to write to the **GPTM TimerB Mode (GPTMTBMR)** register.

When software writes the TAEN bit in the **GPTM Control (GPTMCTL)** register (see page 314), the timer begins counting down from its preloaded value. Once the 0x0000.0000 state is reached, the timer reloads its start value from the concatenated **GPTMTAILR** on the next cycle. If configured to be a one-shot timer, the timer stops counting and clears the TAEN bit in the **GPTMCTL** register. If configured as a periodic timer, it continues counting.

In addition to reloading the count value, the GPTM generates interrupts and triggers when it reaches the 0x000.0000 state. The GPTM sets the TATORIS bit in the GPTM Raw Interrupt Status (GPTMRIS) register (see page 319), and holds it until it is cleared by writing the GPTM Interrupt Clear (GPTMICR) register (see page 321). If the time-out interrupt is enabled in the GPTM Interrupt Mask (GPTMIMR) register (see page 317), the GPTM also sets the TATOMIS bit in the GPTM Masked Interrupt Status (GPTMMIS) register (see page 320). The ADC trigger is enabled by setting the TAOTE bit in GPTMCTL.

If software reloads the **GPTMTAILR** register while the counter is running, the counter loads the new value on the next clock cycle and continues counting from the new value.

If the TASTALL bit in the **GPTMCTL** register is set, the timer freezes counting while the processor is halted by the debugger. The timer resumes counting when the processor resumes execution.

#### 8.3.2.2 32-Bit Real-Time Clock Timer Mode

In Real-Time Clock (RTC) mode, the concatenated versions of the TimerA and TimerB registers are configured as a 32-bit up-counter. When RTC mode is selected for the first time, the counter is loaded with a value of 0x0000.0001. All subsequent load values must be written to the **GPTM TimerA Match (GPTMTAMATCHR)** register (see page 325) by the controller.

The input clock on an even CCP input is required to be 32.768 KHz in RTC mode. The clock signal is then divided down to a 1 Hz rate and is passed along to the input of the 32-bit counter.

When software writes the TAEN bit inthe **GPTMCTL** register, the counter starts counting up from its preloaded value of 0x0000.0001. When the current count value matches the preloaded value in the **GPTMTAMATCHR** register, it rolls over to a value of 0x0000.0000 and continues counting until

either a hardware reset, or it is disabled by software (clearing the TAEN bit). When a match occurs, the GPTM asserts the RTCRIS bit in **GPTMRIS**. If the RTC interrupt is enabled in **GPTMIMR**, the GPTM also sets the RTCMIS bit in **GPTMMIS** and generates a controller interrupt. The status flags are cleared by writing the RTCCINT bit in **GPTMICR**.

If the TASTALL and/or TBSTALL bits in the **GPTMCTL** register are set, the timer does not freeze if the RTCEN bit is set in **GPTMCTL**.

### 8.3.3 16-Bit Timer Operating Modes

The GPTM is placed into global 16-bit mode by writing a value of 0x4 to the **GPTM Configuration** (**GPTMCFG**) register (see page 309). This section describes each of the GPTM 16-bit modes of operation. TimerA and TimerB have identical modes, so a single description is given using an **n** to reference both.

#### 8.3.3.1 16-Bit One-Shot/Periodic Timer Mode

In 16-bit one-shot and periodic timer modes, the timer is configured as a 16-bit down-counter with an optional 8-bit prescaler that effectively extends the counting range of the timer to 24 bits. The selection of one-shot or periodic mode is determined by the value written to the TnMR field of the **GPTMTnMR** register. The optional prescaler is loaded into the **GPTM Timern Prescale (GPTMTnPR)** register.

When software writes the TnEN bit in the **GPTMCTL** register, the timer begins counting down from its preloaded value. Once the 0x0000 state is reached, the timer reloads its start value from **GPTMTnILR** and **GPTMTnPR** on the next cycle. If configured to be a one-shot timer, the timer stops counting and clears the TnEN bit in the **GPTMCTL** register. If configured as a periodic timer, it continues counting.

In addition to reloading the count value, the timer generates interrupts and triggers when it reaches the 0x0000 state. The GPTM sets the TnTORIS bit in the **GPTMRIS** register, and holds it until it is cleared by writing the **GPTMICR** register. If the time-out interrupt is enabled in **GPTMIMR**, the GPTM also sets the TnTOMIS bit in **GPTMISR** and generates a controller interrupt. The ADC trigger is enabled by setting the TnOTE bit in the **GPTMCTL** register.

If software reloads the **GPTMTAILR** register while the counter is running, the counter loads the new value on the next clock cycle and continues counting from the new value.

If the TnSTALL bit in the **GPTMCTL** register is set, the timer freezes counting while the processor is halted by the debugger. The timer resumes counting when the processor resumes execution.

The following example shows a variety of configurations for a 16-bit free running timer while using the prescaler. All values assume a 25-MHz clock with Tc=20 ns (clock period).

Prescale	#Clock (T c) <sup>a</sup>	Max Time	Units
00000000	1	2.6214	mS
0000001	2	5.2428	mS
0000010	3	7.8642	mS
11111101	254	665.8458	mS
11111110	255	668.4672	mS
1111111	256	671.0886	mS

**Table 8-4. 16-Bit Timer With Prescaler Configurations** 

a. Tc is the clock period.

### 8.3.3.2 16-Bit Input Edge Count Mode

**Note:** For rising-edge detection, the input signal must be High for at least two system clock periods following the rising edge. Similarly, for falling-edge detection, the input signal must be Low for at least two system clock periods following the falling edge. Based on this criteria, the maximum input frequency for edge detection is 1/4 of the system frequency.

**Note:** The prescaler is not available in 16-Bit Input Edge Count mode.

In Edge Count mode, the timer is configured as a down-counter capable of capturing three types of events: rising edge, falling edge, or both. To place the timer in Edge Count mode, the TnCMR bit of the GPTMTnMR register must be set to 0. The type of edge that the timer counts is determined by the TnEVENT fields of the GPTMCTL register. During initialization, the GPTM Timern Match (GPTMTnMATCHR) register is configured so that the difference between the value in the GPTMTnILR register and the GPTMTnMATCHR register equals the number of edge events that must be counted.

When software writes the TnEN bit in the **GPTM Control (GPTMCTL)** register, the timer is enabled for event capture. Each input event on the CCP pin decrements the counter by 1 until the event count matches **GPTMTnMATCHR**. When the counts match, the GPTM asserts the CnMRIS bit in the **GPTMRIS** register (and the CnMMIS bit, if the interrupt is not masked).

The counter is then reloaded using the value in **GPTMTnILR**, and stopped since the GPTM automatically clears the TnEN bit in the **GPTMCTL** register. Once the event count has been reached, all further events are ignored until TnEN is re-enabled by software.

Figure 8-2 on page 302 shows how input edge count mode works. In this case, the timer start value is set to **GPTMTnILR** =0x000A and the match value is set to **GPTMTnMATCHR** =0x0006 so that four edge events are counted. The counter is configured to detect both edges of the input signal.

Note that the last two edges are not counted since the timer automatically clears the TnEN bit after the current count matches the value in the **GPTMTnMATCHR** register.




Figure 8-2. 16-Bit Input Edge Count Mode Example

302 November 18, 2011

### 8.3.3.3 16-Bit Input Edge Time Mode

**Note:** For rising-edge detection, the input signal must be High for at least two system clock periods following the rising edge. Similarly, for falling edge detection, the input signal must be Low for at least two system clock periods following the falling edge. Based on this criteria, the maximum input frequency for edge detection is 1/4 of the system frequency.

**Note:** The prescaler is not available in 16-Bit Input Edge Time mode.

In Edge Time mode, the timer is configured as a free-running down-counter initialized to the value loaded in the **GPTMTnILR** register (or 0xFFFF at reset). The timer is capable of capturing three types of events: rising edge, falling edge, or both. The timer is placed into Edge Time mode by setting the TnCMR bit in the **GPTMTnMR** register, and the type of event that the timer captures is determined by the TnEVENT fields of the **GPTMCTL** register.

When software writes the TnEN bit in the **GPTMCTL** register, the timer is enabled for event capture. When the selected input event is detected, the current Tn counter value is captured in the **GPTMTnR** register and is available to be read by the controller. The GPTM then asserts the CnERIS bit (and the CnEMIS bit, if the interrupt is not masked).

After an event has been captured, the timer does not stop counting. It continues to count until the  $\mathtt{TnEN}$  bit is cleared. When the timer reaches the 0x0000 state, it is reloaded with the value from the **GPTMTnILR** register.

Figure 8-3 on page 303 shows how input edge timing mode works. In the diagram, it is assumed that the start value of the timer is the default value of 0xFFFF, and the timer is configured to capture rising edge events.

Each time a rising edge event is detected, the current count value is loaded into the **GPTMTnR** register, and is held there until another rising edge is detected (at which point the new count value is loaded into **GPTMTnR**).

Count GPTMTnR=X GPTMTnR=Z GPTMTnR=Z X Y Time

Figure 8-3. 16-Bit Input Edge Time Mode Example

### 8.3.3.4 16-Bit PWM Mode

Input Signal

**Note:** The prescaler is not available in 16-Bit PWM mode.

The GPTM supports a simple PWM generation mode. In PWM mode, the timer is configured as a down-counter with a start value (and thus period) defined by **GPTMTnILR**. In this mode, the PWM frequency and period are synchronous events and therefore guaranteed to be glitch free. PWM mode is enabled with the **GPTMTnMR** register by setting the TnAMS bit to 0x1, the TnCMR bit to 0x0, and the TnMR field to 0x2.

When software writes the  $\mathtt{TnEN}$  bit in the **GPTMCTL** register, the counter begins counting down until it reaches the 0x0000 state. On the next counter cycle, the counter reloads its start value from **GPTMTnILR** and continues counting until disabled by software clearing the  $\mathtt{TnEN}$  bit in the **GPTMCTL** register. No interrupts or status bits are asserted in PWM mode.

The output PWM signal asserts when the counter is at the value of the **GPTMTnILR** register (its start state), and is deasserted when the counter value equals the value in the **GPTM Timern Match Register (GPTMTnMATCHR)**. Software has the capability of inverting the output PWM signal by setting the TnPWML bit in the **GPTMCTL** register.

Figure 8-4 on page 304 shows how to generate an output PWM with a 1-ms period and a 66% duty cycle assuming a 50-MHz input clock and **TnPWML** =0 (duty cycle would be 33% for the **TnPWML** =1 configuration). For this example, the start value is **GPTMTnIRL**=0xC350 and the match value is **GPTMTnMATCHR**=0x411A.




Figure 8-4. 16-Bit PWM Mode Example

# 8.4 Initialization and Configuration

To use the general-purpose timers, the peripheral clock must be enabled by setting the TIMERO, TIMER1, and TIMER2 bits in the **RCGC1** register.

This section shows module initialization and configuration examples for each of the supported timer modes.

### 8.4.1 32-Bit One-Shot/Periodic Timer Mode

The GPTM is configured for 32-bit One-Shot and Periodic modes by the following sequence:

- 1. Ensure the timer is disabled (the TAEN bit in the **GPTMCTL** register is cleared) before making any changes.
- 2. Write the GPTM Configuration Register (GPTMCFG) with a value of 0x0.
- 3. Set the TAMR field in the GPTM TimerA Mode Register (GPTMTAMR):
  - **a.** Write a value of 0x1 for One-Shot mode.
  - **b.** Write a value of 0x2 for Periodic mode.
- 4. Load the start value into the GPTM TimerA Interval Load Register (GPTMTAILR).
- 5. If interrupts are required, set the TATOIM bit in the GPTM Interrupt Mask Register (GPTMIMR).
- 6. Set the TAEN bit in the GPTMCTL register to enable the timer and start counting.
- 7. Poll the TATORIS bit in the **GPTMRIS** register or wait for the interrupt to be generated (if enabled). In both cases, the status flags are cleared by writing a 1 to the TATOCINT bit of the **GPTM** Interrupt Clear Register (GPTMICR).

In One-Shot mode, the timer stops counting after step 7 on page 305. To re-enable the timer, repeat the sequence. A timer configured in Periodic mode does not stop counting after it times out.

### 8.4.2 32-Bit Real-Time Clock (RTC) Mode

To use the RTC mode, the timer must have a 32.768-KHz input signal on an even CCP input. To enable the RTC feature, follow these steps:

- 1. Ensure the timer is disabled (the TAEN bit is cleared) before making any changes.
- 2. Write the GPTM Configuration Register (GPTMCFG) with a value of 0x1.
- 3. Write the desired match value to the GPTM TimerA Match Register (GPTMTAMATCHR).
- 4. Set/clear the RTCEN bit in the GPTM Control Register (GPTMCTL) as desired.
- 5. If interrupts are required, set the RTCIM bit in the GPTM Interrupt Mask Register (GPTMIMR).
- 6. Set the TAEN bit in the **GPTMCTL** register to enable the timer and start counting.

When the timer count equals the value in the **GPTMTAMATCHR** register, the GPTM asserts the RTCRIS bit in the **GPTMRIS** register and continues counting until Timer A is disabled or a hardware reset. The interrupt is cleared by writing the RTCCINT bit in the **GPTMICR** register.

### 8.4.3 16-Bit One-Shot/Periodic Timer Mode

A timer is configured for 16-bit One-Shot and Periodic modes by the following sequence:

- 1. Ensure the timer is disabled (the TnEN bit is cleared) before making any changes.
- 2. Write the GPTM Configuration Register (GPTMCFG) with a value of 0x4.

- 3. Set the TnMR field in the GPTM Timer Mode (GPTMTnMR) register:
  - **a.** Write a value of 0x1 for One-Shot mode.
  - **b.** Write a value of 0x2 for Periodic mode.
- 4. If a prescaler is to be used, write the prescale value to the **GPTM Timern Prescale Register** (**GPTMTnPR**).
- 5. Load the start value into the GPTM Timer Interval Load Register (GPTMTnILR).
- 6. If interrupts are required, set the Thtoim bit in the GPTM Interrupt Mask Register (GPTMIMR).
- 7. Set the TnEN bit in the **GPTM Control Register (GPTMCTL)** to enable the timer and start counting.
- 8. Poll the TnTORIS bit in the GPTMRIS register or wait for the interrupt to be generated (if enabled). In both cases, the status flags are cleared by writing a 1 to the TnTOCINT bit of the GPTM Interrupt Clear Register (GPTMICR).

In One-Shot mode, the timer stops counting after step 8 on page 306. To re-enable the timer, repeat the sequence. A timer configured in Periodic mode does not stop counting after it times out.

### 8.4.4 16-Bit Input Edge Count Mode

A timer is configured to Input Edge Count mode by the following sequence:

- 1. Ensure the timer is disabled (the TnEN bit is cleared) before making any changes.
- 2. Write the GPTM Configuration (GPTMCFG) register with a value of 0x4.
- 3. In the GPTM Timer Mode (GPTMTnMR) register, write the TnCMR field to 0x0 and the TnMR field to 0x3.
- **4.** Configure the type of event(s) that the timer captures by writing the Tnevent field of the **GPTM Control (GPTMCTL)** register.
- 5. Load the timer start value into the GPTM Timern Interval Load (GPTMTnILR) register.
- 6. Load the desired event count into the GPTM Timern Match (GPTMTnMATCHR) register.
- 7. If interrupts are required, set the CnMIM bit in the GPTM Interrupt Mask (GPTMIMR) register.
- 8. Set the TnEN bit in the **GPTMCTL** register to enable the timer and begin waiting for edge events.
- 9. Poll the CnMRIS bit in the **GPTMRIS** register or wait for the interrupt to be generated (if enabled). In both cases, the status flags are cleared by writing a 1 to the CnMCINT bit of the **GPTM** Interrupt Clear (GPTMICR) register.

In Input Edge Count Mode, the timer stops after the desired number of edge events has been detected. To re-enable the timer, ensure that the TnEN bit is cleared and repeat step 4 on page 306 through step 9 on page 306.

# 8.4.5 16-Bit Input Edge Timing Mode

A timer is configured to Input Edge Timing mode by the following sequence:

- 1. Ensure the timer is disabled (the TnEN bit is cleared) before making any changes.
- 2. Write the **GPTM Configuration (GPTMCFG)** register with a value of 0x4.
- 3. In the GPTM Timer Mode (GPTMTnMR) register, write the TnCMR field to 0x1 and the TnMR field to 0x3.
- **4.** Configure the type of event that the timer captures by writing the Tnevent field of the **GPTM Control (GPTMCTL)** register.
- 5. Load the timer start value into the GPTM Timern Interval Load (GPTMTnILR) register.
- 6. If interrupts are required, set the CnEIM bit in the GPTM Interrupt Mask (GPTMIMR) register.
- 7. Set the Then bit in the GPTM Control (GPTMCTL) register to enable the timer and start counting.
- 8. Poll the Cners bit in the GPTMRIS register or wait for the interrupt to be generated (if enabled). In both cases, the status flags are cleared by writing a 1 to the Cnecint bit of the GPTM Interrupt Clear (GPTMICR) register. The time at which the event happened can be obtained by reading the GPTM Timern (GPTMTnR) register.

In Input Edge Timing mode, the timer continues running after an edge event has been detected, but the timer interval can be changed at any time by writing the **GPTMTnILR** register. The change takes effect at the next cycle after the write.

#### 8.4.6 16-Bit PWM Mode

A timer is configured to PWM mode using the following sequence:

- 1. Ensure the timer is disabled (the TnEN bit is cleared) before making any changes.
- 2. Write the **GPTM Configuration (GPTMCFG)** register with a value of 0x4.
- 3. In the **GPTM Timer Mode (GPTMTnMR)** register, set the TnAMS bit to 0x1, the TnCMR bit to 0x0. and the TnMR field to 0x2.
- **4.** Configure the output state of the PWM signal (whether or not it is inverted) in the TnPWML field of the **GPTM Control (GPTMCTL)** register.
- 5. Load the timer start value into the GPTM Timern Interval Load (GPTMTnILR) register.
- 6. Load the GPTM Timern Match (GPTMTnMATCHR) register with the desired value.
- 7. Set the TnEN bit in the **GPTM Control (GPTMCTL)** register to enable the timer and begin generation of the output PWM signal.

In PWM Timing mode, the timer continues running after the PWM signal has been generated. The PWM period can be adjusted at any time by writing the **GPTMTnILR** register, and the change takes effect at the next cycle after the write.

# 8.5 Register Map

Table 8-5 on page 308 lists the GPTM registers. The offset listed is a hexadecimal increment to the register's address, relative to that timer's base address:

■ Timer0: 0x4003.0000

Timer1: 0x4003.1000Timer2: 0x4003.2000

Note that the Timer module clock must be enabled before the registers can be programmed (see page 210). There must be a delay of 3 system clocks after the Timer module clock is enabled before any Timer module registers are accessed.

Table 8-5. Timers Register Map

Offset	Name	Туре	Reset	Description	See page
0x000	GPTMCFG	R/W	0x0000.0000	GPTM Configuration	309
0x004	GPTMTAMR	R/W	0x0000.0000	GPTM TimerA Mode	310
800x0	GPTMTBMR	R/W	0x0000.0000	GPTM TimerB Mode	312
0x00C	GPTMCTL	R/W	0x0000.0000	GPTM Control	314
0x018	GPTMIMR	R/W	0x0000.0000	GPTM Interrupt Mask	317
0x01C	GPTMRIS	RO	0x0000.0000	GPTM Raw Interrupt Status	319
0x020	GPTMMIS	RO	0x0000.0000	GPTM Masked Interrupt Status	320
0x024	GPTMICR	W1C	0x0000.0000	GPTM Interrupt Clear	321
0x028	GPTMTAILR	R/W	0xFFFF.FFFF	GPTM TimerA Interval Load	323
0x02C	GPTMTBILR	R/W	0x0000.FFFF	GPTM TimerB Interval Load	324
0x030	GPTMTAMATCHR	R/W	0xFFFF.FFFF	GPTM TimerA Match	325
0x034	GPTMTBMATCHR	R/W	0x0000.FFFF	GPTM TimerB Match	326
0x038	GPTMTAPR	R/W	0x0000.0000	GPTM TimerA Prescale	327
0x03C	GPTMTBPR	R/W	0x0000.0000	GPTM TimerB Prescale	328
0x040	GPTMTAPMR	R/W	0x0000.0000	GPTM TimerA Prescale Match	329
0x044	GPTMTBPMR	R/W	0x0000.0000	GPTM TimerB Prescale Match	330
0x048	GPTMTAR	RO	0xFFFF.FFFF	GPTM TimerA	331
0x04C	GPTMTBR	RO	0x0000.FFFF	GPTM TimerB	332

# 8.6 Register Descriptions

The remainder of this section lists and describes the GPTM registers, in numerical order by address offset.


# Register 1: GPTM Configuration (GPTMCFG), offset 0x000

This register configures the global operation of the GPTM module. The value written to this register determines whether the GPTM is in 32- or 16-bit mode.

### GPTM Configuration (GPTMCFG)

Timer0 base: 0x4003.0000 Timer1 base: 0x4003.1000 Timer2 base: 0x4003.2000 Offset 0x000

Type R/W, reset 0x0000.0000



Bit/Field	Name	Type	Reset	Description
31:3	reserved	RO	0x00	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
2:0	GPTMCFG	R/W	0x0	GPTM Configuration

The GPTMCFG values are defined as follows:

Value Description

0x0 32-bit timer configuration.

0x1 32-bit real-time clock (RTC) counter configuration.

0x2 Reserved 0x3 Reserved

0x4-0x7 16-bit timer configuration, function is controlled by bits 1:0 of **GPTMTAMR** and **GPTMTBMR**.

### Register 2: GPTM TimerA Mode (GPTMTAMR), offset 0x004

This register configures the GPTM based on the configuration selected in the **GPTMCFG** register. When in 16-bit PWM mode, set the TAAMS bit to 0x1, the TACMR bit to 0x0, and the TAMR field to 0x2.

### GPTM TimerA Mode (GPTMTAMR)


Name

Timer0 base: 0x4003.0000 Timer1 base: 0x4003.1000 Timer2 base: 0x4003.2000

Offset 0x004

Bit/Field

Type R/W, reset 0x0000.0000



31:4	reserved	RO	0x00	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should by preserved across a read-modify-write operation.
3	TAAMS	R/W	0	GPTM TimerA Alternate Mode Select

Reset

Description

The  ${\tt TAAMS}$  values are defined as follows:

Value Description

Capture mode is enabled.

PWM mode is enabled.

**Note:** To enable PWM mode, you must also clear the TACMR bit and set the TAMR field to 0x2.

be

2 TACMR R/W 0 GPTM TimerA Capture Mode

Type

The TACMR values are defined as follows:

Value Description

D Edge-Count mode

1 Edge-Time mode

Bit/Field	Name	Type	Reset	Description
1:0	TAMR	R/W	0x0	GPTM TimerA Mode
				The TAMR values are defined as follows:
				Value Description
				0x0 Reserved
				0x1 One-Shot Timer mode
				0x2 Periodic Timer mode
				0x3 Capture mode
				The Timer mode is based on the timer configuration defined by bits 2:0 in the <b>GPTMCFG</b> register (16-or 32-bit).
				In 16-bit timer configuration, ${\tt TAMR}$ controls the 16-bit timer modes for TimerA.
				In 32-bit timer configuration, this register controls the mode and the contents of <b>GPTMTBMR</b> are ignored.

### Register 3: GPTM TimerB Mode (GPTMTBMR), offset 0x008

This register configures the GPTM based on the configuration selected in the **GPTMCFG** register. When in 16-bit PWM mode, set the TBAMS bit to 0x1, the TBCMR bit to 0x0, and the TBMR field to 0x2.

### GPTM TimerB Mode (GPTMTBMR)


Name

Timer0 base: 0x4003.0000 Timer1 base: 0x4003.1000 Timer2 base: 0x4003.2000

Offset 0x008

Bit/Field

Type R/W, reset 0x0000.0000



31:4	reserved	RO	0x00	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
3	TBAMS	R/W	0	GPTM TimerB Alternate Mode Select

Reset

Description

Value Description

Capture mode is enabled.

The TBAMS values are defined as follows:

1 PWM mode is enabled.

**Note:** To enable PWM mode, you must also clear the TBCMR bit and set the TBMR field to 0x2.

2 TBCMR R/W 0 GPTM TimerB Capture Mode

Type

The  ${\tt TBCMR}$  values are defined as follows:

Value Description

D Edge-Count mode

1 Edge-Time mode

Bit/Field	Name	Туре	Reset	Description
1:0	TBMR	R/W	0x0	GPTM TimerB Mode The TBMR values are defined as follows:
				Value Description  0x0 Reserved  0x1 One-Shot Timer mode  0x2 Periodic Timer mode
				0x3 Capture mode  The timer mode is based on the timer configuration defined by bits 2:0 in the <b>GPTMCFG</b> register.  In 16-bit timer configuration, these bits control the 16-bit timer modes

In 32-bit timer configuration, this register's contents are ignored and **GPTMTAMR** is used.


November 18, 2011 313

### Register 4: GPTM Control (GPTMCTL), offset 0x00C

This register is used alongside the **GPTMCFG** and **GMTMTnMR** registers to fine-tune the timer configuration, and to enable other features such as timer stall and the output trigger. The output trigger can be used to initiate transfers on the ADC module.

### GPTM Control (GPTMCTL)

Timer0 base: 0x4003.0000 Timer1 base: 0x4003.1000 Timer2 base: 0x4003.2000



preserved across a read-modify-write operation.

Bit/Field	Name	Туре	Reset	Description
11:10	TBEVENT	R/W	0x0	GPTM TimerB Event Mode
				The TBEVENT values are defined as follows:
				Value Description
				0x0 Positive edge
				0x1 Negative edge
				0x2 Reserved
				0x3 Both edges
9	TBSTALL	R/W	0	GPTM Timer B Stall Enable
				The TBSTALL values are defined as follows:
				Value Description
				O Timer B continues counting while the processor is halted by the debugger.
				1 Timer B freezes counting while the processor is halted by the debugger.
				If the processor is executing normally, the ${\tt TBSTALL}$ bit is ignored.
8	TBEN	R/W	0	GPTM TimerB Enable
				The TBEN values are defined as follows:
				Value Description
				0 TimerB is disabled.
				1 TimerB is enabled and begins counting or the capture logic is enabled based on the GPTMCFG register.
7	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
6	TAPWML	R/W	0	GPTM TimerA PWM Output Level
Ü	7.0 ******	1011	ŭ	The TAPWML values are defined as follows:
				Value Description
				0 Output is unaffected.
				1 Output is inverted.
5	TAOTE	R/W	0	GPTM TimerA Output Trigger Enable
				The TAOTE values are defined as follows:
				Value Description
				The output TimerA ADC trigger is disabled.
				The output TimerA ADC trigger is enabled.

source with the  $\mathtt{EMn}$  bit in the **ADCEMUX** register (see page 372).

In addition, the ADC must be enabled and the timer selected as a trigger

November 18, 2011 315

Bit/Field	Name	Туре	Reset	Description
4	RTCEN	R/W	0	GPTM RTC Enable
				The RTCEN values are defined as follows:
				Value Description
				0 RTC counting is disabled.
				1 RTC counting is enabled.
3:2	TAEVENT	R/W	0x0	GPTM TimerA Event Mode
				The TAEVENT values are defined as follows:
				Value Description
				0x0 Positive edge
				0x1 Negative edge
				0x2 Reserved
				0x3 Both edges
1	TASTALL	R/W	0	GPTM Timer A Stall Enable
				The TASTALL values are defined as follows:
				Value Description
				Timer A continues counting while the processor is halted by the debugger.
				Timer A freezes counting while the processor is halted by the debugger.
				If the processor is executing normally, the ${\tt TASTALL}$ bit is ignored.
0	TAEN	R/W	0	GPTM TimerA Enable
				The TAEN values are defined as follows:
				Value Description
				0 TimerA is disabled.

1 TimerA is enabled and begins counting or the capture logic is enabled based on the GPTMCFG register.

# Register 5: GPTM Interrupt Mask (GPTMIMR), offset 0x018

This register allows software to enable/disable GPTM controller-level interrupts. Writing a 1 enables the interrupt, while writing a 0 disables it.

### GPTM Interrupt Mask (GPTMIMR)

Timer0 base: 0x4003.0000
Timer1 base: 0x4003.1000
Timer2 base: 0x4003.2000
Offset 0x018
Type R/W, reset 0x0000.0000

	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16
					' '	1		rese	rved			•			1	•
Type Reset	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0
	15	14	13	12	11	10	9	8	7	6	5	4	3	2	1	0
			reserved		1	CBEIM	СВМІМ	ТВТОІМ		l	rved	1	RTCIM	CAEIM	CAMIM	TATOIM
Type Reset	RO 0	RO 0	RO 0	RO 0	RO 0	R/W 0	R/W 0	R/W 0	RO 0	RO 0	RO 0	RO 0	R/W 0	R/W 0	R/W 0	R/W 0
reset	Ü	Ü	Ü	v	O	Ü	Ü	Ü	Ü	Ü	Ü	Ü	Ü	Ü	Ü	Ü
E	Bit/Field		Nam	ie	Ту	ре	Reset	Des	cription							
	31:11		reserv	/ed	R	0	0x00					he value				
												ucts, the dify-write			ed bit sh	ould be
	10		CBE	IM	R/	W	0	GPT	M Capti	ureB Eve	ent Interr	upt Masl	k			
								The	CBEIM	values a	re define	d as follo	ows:			
								Valu	ue Desc	ription						
								0	Inter	rupt is di	sabled.					
								1	Inter	rupt is er	nabled.					
	9		СВМ	IM	R/	W	0	GPT	M Captı	ureB Ma	tch Inter	rupt Mas	k			
								The	CBMIM	values a	re define	ed as follo	ows:			
								Valu	ue Desc	ription						
								0	Inter	rupt is di	sabled.					
								1	Inter	rupt is er	nabled.					
	8		ТВТС	olM	R/	W	0	GPT	M Time	rB Time-	Out Inte	rrupt Ma	sk			
								The	TBTOIM	values	are defir	ed as fo	llows:			
								Valu	ue Desc	ription						
								0	Inter	rupt is di	sabled.					
								1	Inter	rupt is er	nabled.					
	7:4		reserv	/ed	R	0	0	com	patibility	with fut	ure produ	he value ucts, the dify-write	value of	a reserv		

Bit/Field	Name	Type	Reset	Description
3	RTCIM	R/W	0	GPTM RTC Interrupt Mask The RTCIM values are defined as follows:
				Value Description  0 Interrupt is disabled.  1 Interrupt is enabled.
2	CAEIM	R/W	0	GPTM CaptureA Event Interrupt Mask The CAEIM values are defined as follows:
				Value Description  0 Interrupt is disabled.  1 Interrupt is enabled.
1	CAMIM	R/W	0	GPTM CaptureA Match Interrupt Mask The CAMIM values are defined as follows:
				Value Description  0 Interrupt is disabled.  1 Interrupt is enabled.
0	TATOIM	R/W	0	GPTM TimerA Time-Out Interrupt Mask The TATOIM values are defined as follows:
				Value Description  0 Interrupt is disabled.  1 Interrupt is enabled.

## Register 6: GPTM Raw Interrupt Status (GPTMRIS), offset 0x01C


This register shows the state of the GPTM's internal interrupt signal. These bits are set whether or not the interrupt is masked in the **GPTMIMR** register. Each bit can be cleared by writing a 1 to its corresponding bit in **GPTMICR**.

#### GPTM Raw Interrupt Status (GPTMRIS)

Timer0 base: 0x4003.0000 Timer1 base: 0x4003.1000 Timer2 base: 0x4003.2000

Offset 0x01C

Type RO, reset 0x0000.0000



This the TimerA time-out interrupt status prior to masking.

## Register 7: GPTM Masked Interrupt Status (GPTMMIS), offset 0x020

This register show the state of the GPTM's controller-level interrupt. If an interrupt is unmasked in **GPTMIMR**, and there is an event that causes the interrupt to be asserted, the corresponding bit is set in this register. All bits are cleared by writing a 1 to the corresponding bit in **GPTMICR**.

#### GPTM Masked Interrupt Status (GPTMMIS)

**TATOMIS** 

0


RO

0

Timer0 base: 0x4003.0000 Timer1 base: 0x4003.1000 Timer2 base: 0x4003.2000

Offset 0x020

Type RO, reset 0x0000.0000



**GPTM TimerA Time-Out Masked Interrupt** 

This is the TimerA time-out interrupt status after masking.

# Register 8: GPTM Interrupt Clear (GPTMICR), offset 0x024


This register is used to clear the status bits in the **GPTMRIS** and **GPTMMIS** registers. Writing a 1 to a bit clears the corresponding bit in the GPTMRIS and GPTMMIS registers.

#### GPTM Interrupt Clear (GPTMICR)

Timer0 base: 0x4003.0000 Timer1 base: 0x4003.1000 Timer2 base: 0x4003.2000

Offset 0x024

Type W1C, reset 0x0000.0000



Bit/Field	Name	Туре	Reset	Description
3	RTCCINT	W1C	0	GPTM RTC Interrupt Clear The RTCCINT values are defined as follows:
				Value Description  O The interrupt is unaffected.  1 The interrupt is cleared.
2	CAECINT	W1C	0	GPTM CaptureA Event Interrupt Clear The CAECINT values are defined as follows:
				Value Description  O The interrupt is unaffected.  1 The interrupt is cleared.
1	CAMCINT	W1C	0	GPTM CaptureA Match Interrupt Clear The CAMCINT values are defined as follows:
				Value Description  O The interrupt is unaffected.  1 The interrupt is cleared.
0	TATOCINT	W1C	0	GPTM TimerA Time-Out Interrupt Clear The TATOCINT values are defined as follows:
				Value Description  0 The interrupt is unaffected.  1 The interrupt is cleared.

# Register 9: GPTM TimerA Interval Load (GPTMTAILR), offset 0x028


This register is used to load the starting count value into the timer. When GPTM is configured to one of the 32-bit modes, **GPTMTAILR** appears as a 32-bit register (the upper 16-bits correspond to the contents of the **GPTM TimerB Interval Load (GPTMTBILR)** register). In 16-bit mode, the upper 16 bits of this register read as 0s and have no effect on the state of **GPTMTBILR**.

#### GPTM TimerA Interval Load (GPTMTAILR)

Timer0 base: 0x4003.0000 Timer1 base: 0x4003.1000 Timer2 base: 0x4003.2000

Offset 0x028

Type R/W, reset 0xFFFF.FFF



Bit/Field	Name	Туре	Reset	Description
31:16	TAILRH	R/W	0xFFFF	GPTM TimerA Interval Load Register High
				When configured for 32-bit mode via the <b>GPTMCFG</b> register, the <b>GPTM TimerB Interval Load (GPTMTBILR)</b> register loads this value on a write. A read returns the current value of <b>GPTMTBILR</b> .
				In 16-bit mode, this field reads as 0 and does not have an effect on the state of <b>GPTMTBILR</b> .
15:0	TAILRL	R/W	0xFFFF	GPTM TimerA Interval Load Register Low

For both 16- and 32-bit modes, writing this field loads the counter for TimerA. A read returns the current value of **GPTMTAILR**.


### Register 10: GPTM TimerB Interval Load (GPTMTBILR), offset 0x02C

This register is used to load the starting count value into TimerB. When the GPTM is configured to a 32-bit mode, **GPTMTBILR** returns the current value of TimerB and ignores writes.

### GPTM TimerB Interval Load (GPTMTBILR)

Timer0 base: 0x4003.0000 Timer1 base: 0x4003.1000 Timer2 base: 0x4003.2000 Offset 0x02C

Type R/W, reset 0x0000.FFFF



Bit/Field	Name	Type	Reset	Description
31:16	reserved	RO	0x0000	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
15:0	TBILRL	R/W	0xFFFF	GPTM TimerB Interval Load Register

When the GPTM is not configured as a 32-bit timer, a write to this field updates **GPTMTBILR**. In 32-bit mode, writes are ignored, and reads return the current value of **GPTMTBILR**.

## Register 11: GPTM TimerA Match (GPTMTAMATCHR), offset 0x030

This register is used in 32-bit Real-Time Clock mode and 16-bit PWM and Input Edge Count modes.

#### GPTM TimerA Match (GPTMTAMATCHR)


Name

Timer0 base: 0x4003.0000 Timer1 base: 0x4003.1000 Timer2 base: 0x4003.2000

Offset 0x030

Bit/Field

Type R/W, reset 0xFFFF.FFFF



Description

31:16 TAMRH R/W 0xFFFF GPTM TimerA Match Register High

Reset

When configured for 32-bit Real-Time Clock (RTC) mode via the **GPTMCFG** register, this value is compared to the upper half of **GPTMTAR**, to determine match events.

In 16-bit mode, this field reads as 0 and does not have an effect on the state of **GPTMTBMATCHR**.

15:0 TAMRL R/W 0xFFFF GPTM TimerA Match Register Low

Type

When configured for 32-bit Real-Time Clock (RTC) mode via the **GPTMCFG** register, this value is compared to the lower half of **GPTMTAR**, to determine match events.

When configured for PWM mode, this value along with **GPTMTAILR**, determines the duty cycle of the output PWM signal.

When configured for Edge Count mode, this value along with **GPTMTAILR**, determines how many edge events are counted. The total number of edge events counted is equal to the value in **GPTMTAILR** minus this value.

#### Register 12: GPTM TimerB Match (GPTMTBMATCHR), offset 0x034


This register is used in 16-bit PWM and Input Edge Count modes.

#### GPTM TimerB Match (GPTMTBMATCHR)

Timer0 base: 0x4003.0000 Timer1 base: 0x4003.1000 Timer2 base: 0x4003.2000

Offset 0x034

Type R/W, reset 0x0000.FFFF



Bit/Field	Name	Туре	Reset	Description
31:16	reserved	RO	0x0000	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
15:0	TBMRL	R/W	0xFFFF	GPTM TimerB Match Register Low

When configured for PWM mode, this value along with **GPTMTBILR**, determines the duty cycle of the output PWM signal.

When configured for Edge Count mode, this value along with **GPTMTBILR**, determines how many edge events are counted. The total number of edge events counted is equal to the value in **GPTMTBILR** minus this value.


## Register 13: GPTM TimerA Prescale (GPTMTAPR), offset 0x038

This register allows software to extend the range of the 16-bit timers when operating in one-shot or periodic mode.

#### GPTM TimerA Prescale (GPTMTAPR)

Timer0 base: 0x4003.0000 Timer1 base: 0x4003.1000 Timer2 base: 0x4003.2000 Offset 0x038

Type R/W, reset 0x0000.0000



Bit/Field	Name	Type	Reset	Description
31:8	reserved	RO	0x00	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
7:0	TAPSR	R/W	0x00	GPTM TimerA Prescale

The register loads this value on a write. A read returns the current value of the register.

Refer to Table 8-4 on page 301 for more details and an example.


### Register 14: GPTM TimerB Prescale (GPTMTBPR), offset 0x03C

This register allows software to extend the range of the 16-bit timers when operating in one-shot or periodic mode.

#### GPTM TimerB Prescale (GPTMTBPR)

Timer0 base: 0x4003.0000 Timer1 base: 0x4003.1000 Timer2 base: 0x4003.2000 Offset 0x03C

Type R/W, reset 0x0000.0000



Bit/Field	Name	Type	Reset	Description
31:8	reserved	RO	0x00	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
7:0	TBPSR	R/W	0x00	GPTM TimerB Prescale

The register loads this value on a write. A read returns the current value of this register.

Refer to Table 8-4 on page 301 for more details and an example.

#### Register 15: GPTM TimerA Prescale Match (GPTMTAPMR), offset 0x040

This register effectively extends the range of GPTMTAMATCHR to 24 bits when operating in 16-bit one-shot or periodic mode.

#### GPTM TimerA Prescale Match (GPTMTAPMR)

**TAPSMR** 

R/W


0x00

Timer0 base: 0x4003.0000 Timer1 base: 0x4003.1000 Timer2 base: 0x4003.2000

Offset 0x040

7:0

Type R/W, reset 0x0000.0000



This value is used alongside **GPTMTAMATCHR** to detect timer match events while using a prescaler.

preserved across a read-modify-write operation.

**GPTM TimerA Prescale Match** 

## Register 16: GPTM TimerB Prescale Match (GPTMTBPMR), offset 0x044


This register effectively extends the range of GPTMTBMATCHR to 24 bits when operating in 16-bit one-shot or periodic mode.

#### GPTM TimerB Prescale Match (GPTMTBPMR)

Timer0 base: 0x4003.0000 Timer1 base: 0x4003.1000 Timer2 base: 0x4003.2000

Offset 0x044

Type R/W, reset 0x0000.0000



Bit/Field	Name	туре	Reset	Description
31:8	reserved	RO	0x00	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
7:0	TBPSMR	R/W	0x00	GPTM TimerB Prescale Match

This value is used alongside **GPTMTBMATCHR** to detect timer match events while using a prescaler.


## Register 17: GPTM TimerA (GPTMTAR), offset 0x048

This register shows the current value of the TimerA counter in all cases except for Input Edge Count mode. When in this mode, this register contains the number of edges that have occurred.

#### GPTM TimerA (GPTMTAR)

Timer0 base: 0x4003.0000 Timer1 base: 0x4003.1000 Timer2 base: 0x4003.2000 Offset 0x048

Offset 0x048
Type RO, reset 0xFFF.FFF



Bit/Field	Name	Type	Reset	Description
31:16	TARH	RO	0xFFFF	GPTM TimerA Register High  If the <b>GPTMCFG</b> is in a 32-bit mode, TimerB value is read. If the <b>GPTMCFG</b> is in a 16-bit mode, this is read as zero.
15:0	TARL	RO	0xFFFF	GPTM TimerA Register Low


A read returns the current value of the **GPTM TimerA Count Register**, except in Input Edge-Count mode, when it returns the number of edges that have occurred.


## Register 18: GPTM TimerB (GPTMTBR), offset 0x04C

This register shows the current value of the TimerB counter in all cases except for Input Edge Count mode. When in this mode, this register contains the number of edges that have occurred.

#### GPTM TimerB (GPTMTBR)

Timer0 base: 0x4003.0000 Timer1 base: 0x4003.1000 Timer2 base: 0x4003.2000 Offset 0x04C





Bit/Field	Name	Type	Reset	Description
31:16	reserved	RO	0x0000	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
15:0	TBRL	RO	0xFFFF	GPTM TimerB

A read returns the current value of the **GPTM TimerB Count Register**, except in Input Edge-Count mode, when it returns the number of edges that have occurred.

# 9 Watchdog Timer

A watchdog timer can generate nonmaskable interrupts (NMIs) or a reset when a time-out value is reached. The watchdog timer is used to regain control when a system has failed due to a software error or due to the failure of an external device to respond in the expected way.


The Stellaris® Watchdog Timer module has the following features:

- 32-bit down counter with a programmable load register
- Separate watchdog clock with an enable
- Programmable interrupt generation logic with interrupt masking
- Lock register protection from runaway software
- Reset generation logic with an enable/disable
- User-enabled stalling when the controller asserts the CPU Halt flag during debug

The Watchdog Timer can be configured to generate an interrupt to the controller on its first time-out, and to generate a reset signal on its second time-out. Once the Watchdog Timer has been configured, the lock register can be written to prevent the timer configuration from being inadvertently altered.

## 9.1 Block Diagram

Figure 9-1. WDT Module Block Diagram



## 9.2 Functional Description

The Watchdog Timer module generates the first time-out signal when the 32-bit counter reaches the zero state after being enabled; enabling the counter also enables the watchdog timer interrupt. After the first time-out event, the 32-bit counter is re-loaded with the value of the **Watchdog Timer Load (WDTLOAD)** register, and the timer resumes counting down from that value. Once the Watchdog Timer has been configured, the **Watchdog Timer Lock (WDTLOCK)** register is written, which prevents the timer configuration from being inadvertently altered by software.

If the timer counts down to its zero state again before the first time-out interrupt is cleared, and the reset signal has been enabled (via the WatchdogResetEnable function), the Watchdog timer asserts its reset signal to the system. If the interrupt is cleared before the 32-bit counter reaches its second time-out, the 32-bit counter is loaded with the value in the **WDTLOAD** register, and counting resumes from that value.

If **WDTLOAD** is written with a new value while the Watchdog Timer counter is counting, then the counter is loaded with the new value and continues counting.

Writing to **WDTLOAD** does not clear an active interrupt. An interrupt must be specifically cleared by writing to the **Watchdog Interrupt Clear (WDTICR)** register.

The Watchdog module interrupt and reset generation can be enabled or disabled as required. When the interrupt is re-enabled, the 32-bit counter is preloaded with the load register value and not its last state.

### 9.3 Initialization and Configuration

To use the WDT, its peripheral clock must be enabled by setting the WDT bit in the **RCGC0** register. The Watchdog Timer is configured using the following sequence:

- 1. Load the WDTLOAD register with the desired timer load value.
- 2. If the Watchdog is configured to trigger system resets, set the RESEN bit in the WDTCTL register.
- 3. Set the INTEN bit in the WDTCTL register to enable the Watchdog and lock the control register.

If software requires that all of the watchdog registers are locked, the Watchdog Timer module can be fully locked by writing any value to the **WDTLOCK** register. To unlock the Watchdog Timer, write a value of 0x1ACC.E551.

## 9.4 Register Map

Table 9-1 on page 335 lists the Watchdog registers. The offset listed is a hexadecimal increment to the register's address, relative to the Watchdog Timer base address of 0x4000.0000.

Table 9-1. Watchdog Timer Register Map

Offset	Name	Туре	Reset	Description	See page
0x000	WDTLOAD	R/W	0xFFFF.FFFF	Watchdog Load	337
0x004	WDTVALUE	RO	0xFFFF.FFFF	Watchdog Value	338
0x008	WDTCTL	R/W	0x0000.0000	Watchdog Control	339
0x00C	WDTICR	WO	-	Watchdog Interrupt Clear	340
0x010	WDTRIS	RO	0x0000.0000	Watchdog Raw Interrupt Status	341
0x014	WDTMIS	RO	0x0000.0000	Watchdog Masked Interrupt Status	342
0x418	WDTTEST	R/W	0x0000.0000	Watchdog Test	343
0xC00	WDTLOCK	R/W	0x0000.0000	Watchdog Lock	344
0xFD0	WDTPeriphID4	RO	0x0000.0000	Watchdog Peripheral Identification 4	345
0xFD4	WDTPeriphID5	RO	0x0000.0000	Watchdog Peripheral Identification 5	346
0xFD8	WDTPeriphID6	RO	0x0000.0000	Watchdog Peripheral Identification 6	347
0xFDC	WDTPeriphID7	RO	0x0000.0000	Watchdog Peripheral Identification 7	348
0xFE0	WDTPeriphID0	RO	0x0000.0005	Watchdog Peripheral Identification 0	349
0xFE4	WDTPeriphID1	RO	0x0000.0018	Watchdog Peripheral Identification 1	350
0xFE8	WDTPeriphID2	RO	0x0000.0018	Watchdog Peripheral Identification 2	351

Table 9-1. Watchdog Timer Register Map (continued)

Offset	Name	Туре	Reset	Description	See page
0xFEC	WDTPeriphID3	RO	0x0000.0001	Watchdog Peripheral Identification 3	352
0xFF0	WDTPCellID0	RO	0x0000.000D	Watchdog PrimeCell Identification 0	353
0xFF4	WDTPCellID1	RO	0x0000.00F0	Watchdog PrimeCell Identification 1	354
0xFF8	WDTPCellID2	RO	0x0000.0005	Watchdog PrimeCell Identification 2	355
0xFFC	WDTPCellID3	RO	0x0000.00B1	Watchdog PrimeCell Identification 3	356

## 9.5 Register Descriptions

The remainder of this section lists and describes the WDT registers, in numerical order by address offset.


## Register 1: Watchdog Load (WDTLOAD), offset 0x000

This register is the 32-bit interval value used by the 32-bit counter. When this register is written, the value is immediately loaded and the counter restarts counting down from the new value. If the **WDTLOAD** register is loaded with 0x0000.0000, an interrupt is immediately generated.

#### Watchdog Load (WDTLOAD)

Base 0x4000.0000

Offset 0x000 Type R/W, reset 0xFFFF.FFF



Bit/Field Name Type Reset Description

31:0 WDTLoad R/W 0xFFF.FFFF Watchdog Load Value


## Register 2: Watchdog Value (WDTVALUE), offset 0x004

This register contains the current count value of the timer.

Watchdog Value (WDTVALUE)

Base 0x4000.0000 Offset 0x004

Type RO, reset 0xFFFF.FFF



Bit/Field Name Type Reset Description

31:0 WDTValue RO 0xFFF.FFFF Watchdog Value

Current value of the 32-bit down counter.

## Register 3: Watchdog Control (WDTCTL), offset 0x008


This register is the watchdog control register. The watchdog timer can be configured to generate a reset signal (on second time-out) or an interrupt on time-out.

When the watchdog interrupt has been enabled, all subsequent writes to the control register are ignored. The only mechanism that can re-enable writes is a hardware reset.

#### Watchdog Control (WDTCTL)

Base 0x4000.0000 Offset 0x008

Type R/W, reset 0x0000.0000



Bit/Field	Name	Туре	Reset	Description
31:2	reserved	RO	0x00	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
1	RESEN	R/W	0	Watchdog Reset Enable The RESEN values are defined as follows:  Value Description 0 Disabled.
				1 Enable the Watchdog module reset output.
0	INTEN	R/W	0	Watchdog Interrupt Enable The INTEN values are defined as follows:

#### Value Description


- 0 Interrupt event disabled (once this bit is set, it can only be cleared by a hardware reset).
- 1 Interrupt event enabled. Once enabled, all writes are ignored.

## Register 4: Watchdog Interrupt Clear (WDTICR), offset 0x00C

This register is the interrupt clear register. A write of any value to this register clears the Watchdog interrupt and reloads the 32-bit counter from the **WDTLOAD** register. Value for a read or reset is indeterminate.

#### Watchdog Interrupt Clear (WDTICR)

Base 0x4000.0000 Offset 0x00C Type WO, reset -




Bit/Field	Name	Type	Reset	Description
31:0	WDTIntClr	WO	-	Watchdog Interrupt Clear

## Register 5: Watchdog Raw Interrupt Status (WDTRIS), offset 0x010

This register is the raw interrupt status register. Watchdog interrupt events can be monitored via this register if the controller interrupt is masked.

#### Watchdog Raw Interrupt Status (WDTRIS)

Base 0x4000.0000 Offset 0x010 Type RO, reset 0x0000.0000



Bit/Field	Name	Type	Reset	Description
31:1	reserved	RO	0x00	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
0	WDTRIS	RO	0	Watchdog Raw Interrupt Status


Gives the raw interrupt state (prior to masking) of WDTINTR.

## Register 6: Watchdog Masked Interrupt Status (WDTMIS), offset 0x014

This register is the masked interrupt status register. The value of this register is the logical AND of the raw interrupt bit and the Watchdog interrupt enable bit.

Watchdog Masked Interrupt Status (WDTMIS)

Base 0x4000.0000 Offset 0x014 Type RO, reset 0x0000.0000



Bit/Field	Name	Type	Reset	Description
31:1	reserved	RO	0x00	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
0	WDTMIS	RO	0	Watchdog Masked Interrupt Status


Gives the masked interrupt state (after masking) of the WDTINTR interrupt.

## Register 7: Watchdog Test (WDTTEST), offset 0x418

This register provides user-enabled stalling when the microcontroller asserts the CPU halt flag during debug.

#### Watchdog Test (WDTTEST)

Base 0x4000.0000 Offset 0x418 Type R/W, reset 0x0000.0000



Bit/Field	Name	Туре	Reset	Description
31:9	reserved	RO	0x00	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
8	STALL	R/W	0	Watchdog Stall Enable When set to 1, if the Stellaris microcontroller is stopped with a debugger, the watchdog timer stops counting. Once the microcontroller is restarted, the watchdog timer resumes counting.
7:0	reserved	RO	0x00	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.


#### Register 8: Watchdog Lock (WDTLOCK), offset 0xC00

Writing 0x1ACC.E551 to the **WDTLOCK** register enables write access to all other registers. Writing any other value to the **WDTLOCK** register re-enables the locked state for register writes to all the other registers. Reading the **WDTLOCK** register returns the lock status rather than the 32-bit value written. Therefore, when write accesses are disabled, reading the **WDTLOCK** register returns 0x0000.0001 (when locked; otherwise, the returned value is 0x0000.0000 (unlocked)).

#### Watchdog Lock (WDTLOCK)

Base 0x4000.0000 Offset 0xC00

Type R/W, reset 0x0000.0000



A write of the value 0x1ACC.E551 unlocks the watchdog registers for write access. A write of any other value reapplies the lock, preventing any register updates.

A read of this register returns the following values:


Value Description
0x0000.0001 Locked
0x0000.0000 Unlocked

## Register 9: Watchdog Peripheral Identification 4 (WDTPeriphID4), offset 0xFD0

The WDTPeriphIDn registers are hard-coded and the fields within the register determine the reset value.

Watchdog Peripheral Identification 4 (WDTPeriphID4)

Base 0x4000.0000 Offset 0xFD0 Type RO, reset 0x0000.0000



Bit/Field	Name	Type	Reset	Description
31:8	reserved	RO	0x00	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
7:0	PID4	RO	0x00	WDT Peripheral ID Register[7:0]


#### Register 10: Watchdog Peripheral Identification 5 (WDTPeriphID5), offset 0xFD4

The WDTPeriphIDn registers are hard-coded and the fields within the register determine the reset value.

Watchdog Peripheral Identification 5 (WDTPeriphID5)

Base 0x4000.0000

Offset 0xFD4
Type RO, reset 0x0000.0000




#### Register 11: Watchdog Peripheral Identification 6 (WDTPeriphID6), offset 0xFD8

The WDTPeriphIDn registers are hard-coded and the fields within the register determine the reset value.

Watchdog Peripheral Identification 6 (WDTPeriphID6)

Base 0x4000.0000



# Register 12: Watchdog Peripheral Identification 7 (WDTPeriphID7), offset 0xFDC

The **WDTPeriphIDn** registers are hard-coded and the fields within the register determine the reset value.

Watchdog Peripheral Identification 7 (WDTPeriphID7)

PID7


RO

0x00

Base 0x4000.0000

7:0

Offset 0xFDC Type RO, reset 0x0000.0000




WDT Peripheral ID Register[31:24]

#### Register 13: Watchdog Peripheral Identification 0 (WDTPeriphID0), offset 0xFE0

The WDTPeriphIDn registers are hard-coded and the fields within the register determine the reset value.

Watchdog Peripheral Identification 0 (WDTPeriphID0)

Base 0x4000.0000




#### Register 14: Watchdog Peripheral Identification 1 (WDTPeriphID1), offset 0xFE4

The WDTPeriphIDn registers are hard-coded and the fields within the register determine the reset value.

Watchdog Peripheral Identification 1 (WDTPeriphID1)

Base 0x4000.0000

Offset 0xFE4
Type RO, reset 0x0000.0018




Bit/Field	Name	Type	Reset	Description
31:8	reserved	RO	0x00	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
7:0	PID1	RΟ	0v18	Watchdog Perinheral ID Register[15:8]

#### Register 15: Watchdog Peripheral Identification 2 (WDTPeriphID2), offset 0xFE8

The WDTPeriphIDn registers are hard-coded and the fields within the register determine the reset value.

Watchdog Peripheral Identification 2 (WDTPeriphID2)

Base 0x4000.0000




#### Register 16: Watchdog Peripheral Identification 3 (WDTPeriphID3), offset 0xFEC

The WDTPeriphIDn registers are hard-coded and the fields within the register determine the reset value.

Watchdog Peripheral Identification 3 (WDTPeriphID3)

Base 0x4000.0000

Offset 0xFEC Type RO, reset 0x0000.0001




## Register 17: Watchdog PrimeCell Identification 0 (WDTPCellID0), offset 0xFF0

The WDTPCellIDn registers are hard-coded and the fields within the register determine the reset value.

Watchdog PrimeCell Identification 0 (WDTPCellID0)

Base 0x4000.0000 Offset 0xFF0 Type RO, reset 0x0000.000D




Bit/Field	Name	Type	Reset	Description
31:8	reserved	RO	0x00	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
7:0	CID0	RO	0x0D	Watchdog PrimeCell ID Register[7:0]

## Register 18: Watchdog PrimeCell Identification 1 (WDTPCellID1), offset 0xFF4

The WDTPCellIDn registers are hard-coded and the fields within the register determine the reset value.

Watchdog PrimeCell Identification 1 (WDTPCellID1)

Base 0x4000.0000 Offset 0xFF4 Type RO, reset 0x0000.00F0




Bit/Field	Name	Туре	Reset	Description
31:8	reserved	RO	0x00	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
7:0	CID1	RO	0xF0	Watchdog PrimeCell ID Register[15:8]

## Register 19: Watchdog PrimeCell Identification 2 (WDTPCellID2), offset 0xFF8

The WDTPCellIDn registers are hard-coded and the fields within the register determine the reset value.

Watchdog PrimeCell Identification 2 (WDTPCellID2)

Base 0x4000.0000 Offset 0xFF8 Type RO, reset 0x0000.0005




Bit/Field	Name	Type	Reset	Description
31:8	reserved	RO	0x00	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
7:0	CID2	RO	0x05	Watchdog PrimeCell ID Register[23:16]

## Register 20: Watchdog PrimeCell Identification 3 (WDTPCellID3), offset 0xFFC

The WDTPCellIDn registers are hard-coded and the fields within the register determine the reset value.

Watchdog PrimeCell Identification 3 (WDTPCellID3)

Base 0x4000.0000 Offset 0xFFC Type RO, reset 0x0000.00B1



Bit/Field	Name	Туре	Reset	Description
31:8	reserved	RO	0x00	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
7:0	CID3	RO	0xB1	Watchdog PrimeCell ID Register[31:24]

## 10 Analog-to-Digital Converter (ADC)

An analog-to-digital converter (ADC) is a peripheral that converts a continuous analog voltage to a discrete digital number.

The Stellaris® ADC module features 10-bit conversion resolution and supports two input channels, plus an internal temperature sensor. The ADC module contains four programmable sequencer which allows for the sampling of multiple analog input sources without controller intervention. Each sample sequence provides flexible programming with fully configurable input source, trigger events, interrupt generation, and sequence priority.

The Stellaris ADC module provides the following features:

- Two analog input channels
- Single-ended and differential-input configurations
- On-chip internal temperature sensor
- Sample rate of 250 thousand samples/second
- Flexible, configurable analog-to-digital conversion
- Four programmable sample conversion sequences from one to eight entries long, with corresponding conversion result FIFOs
- Flexible trigger control
  - Controller (software)
  - Timers
  - Analog Comparators
  - GPIO
- Hardware averaging of up to 64 samples for improved accuracy
- Converter uses an internal 3-V reference
- Power and ground for the analog circuitry is separate from the digital power and ground

## 10.1 Block Diagram

Figure 10-1 on page 358 provides details on the internal configuration of the ADC controls and data registers.




Figure 10-1. ADC Module Block Diagram

## 10.2 Signal Description

Table 10-1 on page 358 and Table 10-2 on page 358 list the external signals of the ADC module and describe the function of each. The signals are analog functions for some GPIO signals. The column in the table below titled "Pin Assignment" lists the GPIO pin placement for the ADC signals. The AINx analog signals are not 5-V tolerant and go through an isolation circuit before reaching their circuitry. These signals are configured by clearing the corresponding DEN bit in the GPIO Digital Enable (GPIODEN) register and setting the corresponding AMSEL bit in the GPIO Analog Mode Select (GPIOAMSEL) register. For more information on configuring GPIOs, see "General-Purpose Input/Outputs (GPIOs)" on page 251.

Table 10-1. ADC Signals (100LQFP)

Pin Name	Pin Number	Pin Type	Buffer Type <sup>a</sup>	Description
ADC0	1	I	Analog	Analog-to-digital converter input 0.
ADC1	2	I	Analog	Analog-to-digital converter input 1.

a. The TTL designation indicates the pin has TTL-compatible voltage levels.

Table 10-2. ADC Signals (108BGA)

Pin Name	Pin Number	Pin Type	Buffer Type <sup>a</sup>	Description
ADC0	B1	I	Analog	Analog-to-digital converter input 0.
ADC1	A1	I	Analog	Analog-to-digital converter input 1.

a. The TTL designation indicates the pin has TTL-compatible voltage levels.

#### 10.3 **Functional Description**

The Stellaris ADC collects sample data by using a programmable sequence-based approach instead of the traditional single or double-sampling approaches found on many ADC modules. Each sample sequence is a fully programmed series of consecutive (back-to-back) samples, allowing the ADC to collect data from multiple input sources without having to be re-configured or serviced by the controller. The programming of each sample in the sample sequence includes parameters such as the input source and mode (differential versus single-ended input), interrupt generation on sample completion, and the indicator for the last sample in the sequence.

#### 10.3.1 Sample Sequencers

The sampling control and data capture is handled by the sample seguencers. All of the sequencers are identical in implementation except for the number of samples that can be captured and the depth of the FIFO. Table 10-3 on page 359 shows the maximum number of samples that each sequencer can capture and its corresponding FIFO depth. In this implementation, each FIFO entry is a 32-bit word, with the lower 10 bits containing the conversion result.

Sequencer **Number of Samples Depth of FIFO** SS3 1

Table 10-3. Samples and FIFO Depth of Sequencers

SS2 4 4 SS1 4 4 SS0 8 8

For a given sample sequence, each sample is defined by two 4-bit nibbles in the ADC Sample Sequence Input Multiplexer Select (ADCSSMUXn) and ADC Sample Sequence Control (ADCSSCTLn) registers, where "n" corresponds to the sequence number. The ADCSSMUXn nibbles select the input pin, while the ADCSSCTLn nibbles contain the sample control bits corresponding to parameters such as temperature sensor selection, interrupt enable, end of sequence, and differential input mode. Sample sequencers are enabled by setting the respective ASENn bit in the ADC Active Sample Sequencer (ADCACTSS) register, and should be configured before being enabled.

When configuring a sample sequence, multiple uses of the same input pin within the same sequence is allowed. In the ADCSSCTLn register, the IEn bits can be set for any combination of samples, allowing interrupts to be generated after every sample in the sequence if necessary. Also, the END bit can be set at any point within a sample sequence. For example, if Sequencer 0 is used, the END bit can be set in the nibble associated with the fifth sample, allowing Sequencer 0 to complete execution of the sample sequence after the fifth sample.

After a sample sequence completes execution, the result data can be retrieved from the ADC Sample Sequence Result FIFO (ADCSSFIFOn) registers. The FIFOs are simple circular buffers that read a single address to "pop" result data. For software debug purposes, the positions of the FIFO head and tail pointers are visible in the ADC Sample Sequence FIFO Status (ADCSSFSTATn) registers along with FULL and EMPTY status flags. Overflow and underflow conditions are monitored using the ADCOSTAT and ADCUSTAT registers.

#### 10.3.2 **Module Control**

Outside of the sample sequencers, the remainder of the control logic is responsible for tasks such as:

- Interrupt generation
- Sequence prioritization
- Trigger configuration

Most of the ADC control logic runs at the ADC clock rate of 14-18 MHz. The internal ADC divider is configured automatically by hardware when the system XTAL is selected. The automatic clock divider configuration targets 16.667 MHz operation for all Stellaris devices.

#### 10.3.2.1 Interrupts

The register configurations of the sample sequencers dictate which events generate raw interrupts, but do not have control over whether the interrupt is actually sent to the interrupt controller. The ADC module's interrupt signals are controlled by the state of the MASK bits in the ADC Interrupt Mask (ADCIM) register. Interrupt status can be viewed at two locations: the ADC Raw Interrupt Status (ADCRIS) register, which shows the raw status of the various interrupt signals, and the ADC Interrupt Status and Clear (ADCISC) register, which shows active interrupts that are enabled by the ADCIM register. Sequencer interrupts are cleared by writing a 1 to the corresponding IN bit in ADCISC.

#### 10.3.2.2 Prioritization

When sampling events (triggers) happen concurrently, they are prioritized for processing by the values in the ADC Sample Sequencer Priority (ADCSSPRI) register. Valid priority values are in the range of 0-3, with 0 being the highest priority and 3 being the lowest. Multiple active sample sequencer units with the same priority do not provide consistent results, so software must ensure that all active sample sequencer units have a unique priority value.

#### 10.3.2.3 Sampling Events

Sample triggering for each sample sequencer is defined in the **ADC Event Multiplexer Select (ADCEMUX)** register. The external peripheral triggering sources vary by Stellaris family member, but all devices share the "Controller" and "Always" triggers. Software can initiate sampling by setting the SSx bits in the **ADC Processor Sample Sequence Initiate (ADCPSSI)** register.

Care must be taken when using the "Always" trigger. If a sequence's priority is too high, it is possible to starve other lower priority sequences.

#### 10.3.3 Hardware Sample Averaging Circuit

Higher precision results can be generated using the hardware averaging circuit, however, the improved results are at the cost of throughput. Up to 64 samples can be accumulated and averaged to form a single data entry in the sequencer FIFO. Throughput is decreased proportionally to the number of samples in the averaging calculation. For example, if the averaging circuit is configured to average 16 samples, the throughput is decreased by a factor of 16.

By default the averaging circuit is off and all data from the converter passes through to the sequencer FIFO. The averaging hardware is controlled by the **ADC Sample Averaging Control (ADCSAC)** register (see page 379). There is a single averaging circuit and all input channels receive the same amount of averaging whether they are single-ended or differential.

#### 10.3.4 Analog-to-Digital Converter

The converter itself generates a 10-bit output value for selected analog input. Special analog pads are used to minimize the distortion on the input. An internal 3 V reference is used by the converter

resulting in sample values ranging from 0x000 at 0 V input to 0x3FF at 3 V input when in single-ended input mode.

## 10.3.5 Differential Sampling

In addition to traditional single-ended sampling, the ADC module supports differential sampling of two analog input channels. To enable differential sampling, software must set the  $\mathtt{Dn}$  bit in the **ADCSSCTL0n** register in a step's configuration nibble.

When a sequence step is configured for differential sampling, its corresponding value in the **ADCSSMUXn** register must be set to one of the four differential pairs, numbered 0-3. Differential pair 0 samples analog inputs 0 and 1; differential pair 1 samples analog inputs 2 and 3; and so on (see Table 10-4 on page 361). The ADC does not support other differential pairings such as analog input 0 with analog input 3. The number of differential pairs supported is dependent on the number of analog inputs (see Table 10-4 on page 361).

Table 10-4. Differential Sampling Pairs

Differential Pair	Analog Inputs
0	0 and 1

The voltage sampled in differential mode is the difference between the odd and even channels:  $\Delta V$  (differential voltage) =  $V_{IN}$  (even channels) –  $V_{IN}$  (odd channels), therefore:

- If  $\Delta V = 0$ , then the conversion result = 0x1FF
- If  $\Delta V > 0$ , then the conversion result > 0x1FF (range is 0x1FF–0x3FF)
- If  $\Delta V < 0$ , then the conversion result < 0x1FF (range is 0–0x1FF)

The differential pairs assign polarities to the analog inputs: the even-numbered input is always positive, and the odd-numbered input is always negative. In order for a valid conversion result to appear, the negative input must be in the range of  $\pm$  1.5 V of the positive input. If an analog input is greater than 3 V or less than 0 V (the valid range for analog inputs), the input voltage is clipped, meaning it appears as either 3 V or 0 V, respectively, to the ADC.

Figure 10-2 on page 362 shows an example of the negative input centered at 1.5 V. In this configuration, the differential range spans from -1.5 V to 1.5 V. Figure 10-3 on page 362 shows an example where the negative input is centered at -0.75 V, meaning inputs on the positive input saturate past a differential voltage of -0.75 V since the input voltage is less than 0 V. Figure 10-4 on page 363 shows an example of the negative input centered at 2.25 V, where inputs on the positive channel saturate past a differential voltage of 0.75 V since the input voltage would be greater than 3 V.

Figure 10-2. Differential Sampling Range,  $V_{IN\_ODD}$  = 1.5 V





Figure 10-3. Differential Sampling Range,  $V_{IN\_ODD}$  = 0.75 V






Figure 10-4. Differential Sampling Range,  $V_{IN\ ODD}$  = 2.25 V

#### 10.3.6 Test Modes

There is a user-available test mode that allows for loopback operation within the digital portion of the ADC module. This can be useful for debugging software without having to provide actual analog stimulus. This mode is available through the **ADC Test Mode Loopback (ADCTMLB)** register (see page 392).

#### 10.3.7 Internal Temperature Sensor

The temperature sensor's primary purpose is to notify the system that the internal temperature is too high or low for reliable operation.

The temperature sensor does not have a separate enable, since it also contains the bandgap reference and must always be enabled. The reference is supplied to other analog modules; not just the ADC.

The internal temperature sensor provides an analog temperature reading as well as a reference voltage. The voltage at the output terminal SENSO is given by the following equation:

$$SENSO = 2.7 - ((T + 55) / 75)$$

This relation is shown in Figure 10-5 on page 364.




Figure 10-5. Internal Temperature Sensor Characteristic

# 10.4 Initialization and Configuration

In order for the ADC module to be used, the PLL must be enabled and using a supported crystal frequency (see the **RCC** register). Using unsupported frequencies can cause faulty operation in the ADC module.

#### 10.4.1 Module Initialization

Initialization of the ADC module is a simple process with very few steps. The main steps include enabling the clock to the ADC and reconfiguring the sample sequencer priorities (if needed).

The initialization sequence for the ADC is as follows:

- 1. Enable the ADC clock by writing a value of 0x0001.0000 to the **RCGC0** register (see page 204).
- 2. If required by the application, reconfigure the sample sequencer priorities in the **ADCSSPRI** register. The default configuration has Sample Sequencer 0 with the highest priority, and Sample Sequencer 3 as the lowest priority.

#### 10.4.2 Sample Sequencer Configuration

Configuration of the sample sequencers is slightly more complex than the module initialization since each sample sequence is completely programmable.

The configuration for each sample sequencer should be as follows:

- 1. Ensure that the sample sequencer is disabled by writing a 0 to the corresponding ASENn bit in the **ADCACTSS** register. Programming of the sample sequencers is allowed without having them enabled. Disabling the sequencer during programming prevents erroneous execution if a trigger event were to occur during the configuration process.
- 2. Configure the trigger event for the sample sequencer in the ADCEMUX register.
- **3.** For each sample in the sample sequence, configure the corresponding input source in the **ADCSSMUXn** register.

- **4.** For each sample in the sample sequence, configure the sample control bits in the corresponding nibble in the **ADCSSCTLn** register. When programming the last nibble, ensure that the END bit is set. Failure to set the END bit causes unpredictable behavior.
- 5. If interrupts are to be used, write a 1 to the corresponding MASK bit in the ADCIM register.
- **6.** Enable the sample sequencer logic by writing a 1 to the corresponding ASENn bit in the **ADCACTSS** register.

# 10.5 Register Map

Table 10-5 on page 365 lists the ADC registers. The offset listed is a hexadecimal increment to the register's address, relative to the ADC base address of 0x4003.8000.

Note that the ADC module clock must be enabled before the registers can be programmed (see page 204). There must be a delay of 3 system clocks after the ADC module clock is enabled before any ADC module registers are accessed.

Table 10-5. ADC Register Map

Offset	Name	Туре	Reset	Description	See page
0x000	ADCACTSS	R/W	0x0000.0000	ADC Active Sample Sequencer	367
0x004	ADCRIS	RO	0x0000.0000	ADC Raw Interrupt Status	368
0x008	ADCIM	R/W	0x0000.0000	ADC Interrupt Mask	369
0x00C	ADCISC	R/W1C	0x0000.0000	ADC Interrupt Status and Clear	370
0x010	ADCOSTAT	R/W1C	0x0000.0000	ADC Overflow Status	371
0x014	ADCEMUX	R/W	0x0000.0000	ADC Event Multiplexer Select	372
0x018	ADCUSTAT	R/W1C	0x0000.0000	ADC Underflow Status	375
0x020	ADCSSPRI	R/W	0x0000.3210	ADC Sample Sequencer Priority	376
0x028	ADCPSSI	WO	-	ADC Processor Sample Sequence Initiate	378
0x030	ADCSAC	R/W	0x0000.0000	ADC Sample Averaging Control	379
0x040	ADCSSMUX0	R/W	0x0000.0000	ADC Sample Sequence Input Multiplexer Select 0	380
0x044	ADCSSCTL0	R/W	0x0000.0000	ADC Sample Sequence Control 0	382
0x048	ADCSSFIFO0	RO	-	ADC Sample Sequence Result FIFO 0	385
0x04C	ADCSSFSTAT0	RO	0x0000.0100	ADC Sample Sequence FIFO 0 Status	386
0x060	ADCSSMUX1	R/W	0x0000.0000	ADC Sample Sequence Input Multiplexer Select 1	387
0x064	ADCSSCTL1	R/W	0x0000.0000	ADC Sample Sequence Control 1	388
0x068	ADCSSFIFO1	RO	-	ADC Sample Sequence Result FIFO 1	385
0x06C	ADCSSFSTAT1	RO	0x0000.0100	ADC Sample Sequence FIFO 1 Status	386
0x080	ADCSSMUX2	R/W	0x0000.0000	ADC Sample Sequence Input Multiplexer Select 2	387
0x084	ADCSSCTL2	R/W	0x0000.0000	ADC Sample Sequence Control 2	388
0x088	ADCSSFIFO2	RO	-	ADC Sample Sequence Result FIFO 2	385

Table 10-5. ADC Register Map (continued)

Offset	Name	Туре	Reset	Description	See page
0x08C	ADCSSFSTAT2	RO	0x0000.0100	ADC Sample Sequence FIFO 2 Status	386
0x0A0	ADCSSMUX3	R/W	0x0000.0000	ADC Sample Sequence Input Multiplexer Select 3	390
0x0A4	ADCSSCTL3	R/W	0x0000.0002	ADC Sample Sequence Control 3	391
0x0A8	ADCSSFIFO3	RO	-	ADC Sample Sequence Result FIFO 3	385
0x0AC	ADCSSFSTAT3	RO	0x0000.0100	ADC Sample Sequence FIFO 3 Status	386
0x100	ADCTMLB	R/W	0x0000.0000	ADC Test Mode Loopback	392

# 10.6 Register Descriptions


The remainder of this section lists and describes the ADC registers, in numerical order by address offset.

# Register 1: ADC Active Sample Sequencer (ADCACTSS), offset 0x000

This register controls the activation of the sample sequencers. Each sample sequencer can be enabled or disabled independently.

ADC Active Sample Sequencer (ADCACTSS)

Base 0x4003.8000 Offset 0x000 Type R/W, reset 0x0000.0000




Bit/Field	Name	Type	Reset	Description
31:4	reserved	RO	0x0000.000	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
3	ASEN3	R/W	0	ADC SS3 Enable Specifies whether Sample Sequencer 3 is enabled. If set, the sample sequence logic for Sequencer 3 is active. Otherwise, the sequencer is inactive.
2	ASEN2	R/W	0	ADC SS2 Enable Specifies whether Sample Sequencer 2 is enabled. If set, the sample sequence logic for Sequencer 2 is active. Otherwise, the sequencer is inactive.
1	ASEN1	R/W	0	ADC SS1 Enable  Specifies whether Sample Sequencer 1 is enabled. If set, the sample sequence logic for Sequencer 1 is active. Otherwise, the sequencer is inactive.
0	ASEN0	R/W	0	ADC SS0 Enable Specifies whether Sample Sequencer 0 is enabled. If set, the sample sequence logic for Sequencer 0 is active. Otherwise, the sequencer is inactive.

### Register 2: ADC Raw Interrupt Status (ADCRIS), offset 0x004

This register shows the status of the raw interrupt signal of each sample sequencer. These bits may be polled by software to look for interrupt conditions without having to generate controller interrupts.

#### ADC Raw Interrupt Status (ADCRIS)

Base 0x4003.8000 Offset 0x004 Type RO, reset 0x0000.0000



Bit/Field	Name	Туре	Reset	Description
31:4	reserved	RO	0x000	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
3	INR3	RO	0	SS3 Raw Interrupt Status
				This bit is set by hardware when a sample with its respective <b>ADCSSCTL3</b> IE bit has completed conversion. This bit is cleared by setting the IN3 bit in the <b>ADCISC</b> register.
2	INR2	RO	0	SS2 Raw Interrupt Status
				This bit is set by hardware when a sample with its respective <b>ADCSSCTL2</b> IE bit has completed conversion. This bit is cleared by setting the IN2 bit in the <b>ADCISC</b> register.
1	INR1	RO	0	SS1 Raw Interrupt Status
				This bit is set by hardware when a sample with its respective <b>ADCSSCTL1</b> IE bit has completed conversion. This bit is cleared by setting the IN1 bit in the <b>ADCISC</b> register.
0	INR0	RO	0	SS0 Raw Interrupt Status
				This bit is set by hardware when a sample with its respective  ADCSSCTL0 IE bit has completed conversion. This bit is cleared by

setting the IN30 bit in the ADCISC register.

# Register 3: ADC Interrupt Mask (ADCIM), offset 0x008

Reset

This register controls whether the sample sequencer raw interrupt signals are promoted to controller interrupts. Each raw interrupt signal can be masked independently.


#### ADC Interrupt Mask (ADCIM)

Name

Type

Bit/Field

Base 0x4003.8000 Offset 0x008 Type R/W, reset 0x0000.0000



Description

31:4	reserved	RO	0x000	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
3	MASK3	R/W	0	SS3 Interrupt Mask
				When set, this bit allows the raw interrupt signal from Sample Sequencer 3 (ADCRIS register INR3 bit) to be promoted to a controller interrupt.
				When clear, the status of Sample Sequencer 3 does not affect the SS3 interrupt status.
2	MASK2	R/W	0	SS2 Interrupt Mask
				When set, this bit allows the raw interrupt signal from Sample Sequencer 2 (ADCRIS register INR2 bit) to be promoted to a controller interrupt.
				When clear, the status of Sample Sequencer 2 does not affect the SS2 interrupt status.
1	MASK1	R/W	0	SS1 Interrupt Mask
				When set, this bit allows the raw interrupt signal from Sample Sequencer 1 (ADCRIS register INR1 bit) to be promoted to a controller interrupt.
				When clear, the status of Sample Sequencer 1 does not affect the SS1 interrupt status.
0	MASK0	R/W	0	SS0 Interrupt Mask
				When set, this bit allows the raw interrupt signal from Sample Sequencer 0 (ADCRIS register INR0 bit) to be promoted to a controller interrupt.
				When clear, the status of Sample Sequencer 0 does not affect the SS0

interrupt status.


# Register 4: ADC Interrupt Status and Clear (ADCISC), offset 0x00C

This register provides the mechanism for clearing sample sequence interrupt conditions and shows the status of controller interrupts generated by the sample sequencers. When read, each bit field is the logical AND of the respective INR and MASK bits. Sample sequence nterrupts are cleared by setting the corresponding bit position. If software is polling the **ADCRIS** instead of generating interrupts, the sample sequence INR bits are still cleared via the **ADCISC** register, even if the IN bit is not set.

#### ADC Interrupt Status and Clear (ADCISC)

Base 0x4003.8000 Offset 0x00C

Type R/W1C, reset 0x0000.0000



Bit/Field	Name	Type	Reset	Description
31:4	reserved	RO	0x000	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
3	IN3	R/W1C	0	SS3 Interrupt Status and Clear
				This bit is set when both the INR3 bit in the <b>ADCRIS</b> register and the MASK3 bit in the <b>ADCIM</b> register are set, providing a level-based interrupt to the controller.
				This bit is cleared by writing a 1. Clearing this bit also clears the ${\tt INR3}$ bit.
2	IN2	R/W1C	0	SS2 Interrupt Status and Clear
				This bit is set when both the INR2 bit in the <b>ADCRIS</b> register and the MASK2 bit in the <b>ADCIM</b> register are set, providing a level-based interrupt to the controller.
				This bit is cleared by writing a 1. Clearing this bit also clears the ${\tt INR2}$ bit.
1	IN1	R/W1C	0	SS1 Interrupt Status and Clear
				This bit is set when both the INR1 bit in the <b>ADCRIS</b> register and the MASK1 bit in the <b>ADCIM</b> register are set, providing a level-based interrupt to the controller.
				This bit is cleared by writing a 1. Clearing this bit also clears the ${\tt INR1}$ bit.
0	IN0	R/W1C	0	SS0 Interrupt Status and Clear
				This bit is set when both the INRO bit in the <b>ADCRIS</b> register and the MASKO bit in the <b>ADCIM</b> register are set, providing a level-based interrupt to the controller.

This bit is cleared by writing a 1. Clearing this bit also clears the  ${\tt INR0}$ 


# Register 5: ADC Overflow Status (ADCOSTAT), offset 0x010

This register indicates overflow conditions in the sample sequencer FIFOs. Once the overflow condition has been handled by software, the condition can be cleared by writing a 1 to the corresponding bit position.

#### ADC Overflow Status (ADCOSTAT)

Base 0x4003.8000

Offset 0x010 Type R/W1C, reset 0x0000.0000



Bit/Field	Name	Туре	Reset	Description
31:4	reserved	RO	0x0000.000	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
3	OV3	R/W1C	0	SS3 FIFO Overflow
				When set, this bit specifies that the FIFO for Sample Sequencer 3 has hit an overflow condition where the FIFO is full and a write was requested. When an overflow is detected, the most recent write is dropped.
				This bit is cleared by writing a 1.
2	OV2	R/W1C	0	SS2 FIFO Overflow
				When set, this bit specifies that the FIFO for Sample Sequencer 2 has hit an overflow condition where the FIFO is full and a write was requested. When an overflow is detected, the most recent write is dropped.
				This bit is cleared by writing a 1.
1	OV1	R/W1C	0	SS1 FIFO Overflow
				When set, this bit specifies that the FIFO for Sample Sequencer 1 has hit an overflow condition where the FIFO is full and a write was requested. When an overflow is detected, the most recent write is dropped.  This bit is cleared by writing a 1.
0	OV0	R/W1C	0	SS0 FIFO Overflow
Ū	000	10,0010	Ü	When set, this bit specifies that the FIFO for Sample Sequencer 0 has hit an overflow condition where the FIFO is full and a write was requested. When an overflow is detected, the most recent write is dropped.

November 18, 2011 371


This bit is cleared by writing a 1.

# Register 6: ADC Event Multiplexer Select (ADCEMUX), offset 0x014

The ADCEMUX selects the event (trigger) that initiates sampling for each sample sequencer. Each sample sequencer can be configured with a unique trigger source.

#### ADC Event Multiplexer Select (ADCEMUX)

Base 0x4003.8000 Offset 0x014 Type R/W, reset 0x0000.0000



Bit/Field	Name	Туре	Reset	Description
31:16	reserved	RO	0x0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
15:12	EM3	R/W	0x0	SS3 Trigger Select

This field selects the trigger source for Sample Sequencer 3.

The valid configurations for this field are:

Value	Event
0x0	Controller (default)
0x1	Analog Comparator 0
0x2	Analog Comparator 1
0x3	Reserved
0x4	External (GPIO PB4)
0x5	Timer
	In addition, the trigger must be enabled with the ${\tt TnOTE}$ bit in the ${\tt GPTMCTL}$ register (see page 314).
0x6	reserved
0x7	reserved
8x0	reserved
0x9-0xE	reserved
0xF	Always (continuously sample)

Bit/Field	Name	Туре	Reset	Description	
11:8	EM2	R/W	0x0	SS2 Trigger Select	
				This field selects the trigger source for Sample Sequencer 2.	
				The valid configurations for this field are:	
				Value Event	
				0x0 Controller (default)	
				0x1 Analog Comparator 0	
				0x2 Analog Comparator 1	
				0x3 Reserved	
				0x4 External (GPIO PB4)	
				0x5 Timer	
				In addition, the trigger must be enabled with the $\mathtt{TnOTE}$ bit the <b>GPTMCTL</b> register (see page 314).	t in
				0x6 reserved	
				0x7 reserved	
				0x8 reserved	
				0x9-0xE reserved	
				0xF Always (continuously sample)	
7:4	EM1	R/W	0x0	SS1 Trigger Select	
7.4	LIVIT	1000	OXO	This field selects the trigger source for Sample Sequencer 1.	
				The valid configurations for this field are:	
				Value Event	
				0x0 Controller (default)	
				0x1 Analog Comparator 0	
				0x2 Analog Comparator 1	
				0x3 Reserved	
				0x4 External (GPIO PB4)	
				0x5 Timer	
				In addition, the trigger must be enabled with the ${\tt TnOTE}$ bit the <b>GPTMCTL</b> register (see page 314).	t in
				0x6 reserved	
				0x7 reserved	
				0x8 reserved	
				0x9-0xE reserved	
				0xF Always (continuously sample)	


Bit/Field	Name	Type	Reset	Descript	ion
3:0	EM0	R/W	0x0	SS0 Trigger Select This field selects the trigger source for Sample Sequencer 0. The valid configurations for this field are:	
				Value	Event
				0x0	Controller (default)
				0x1	Analog Comparator 0
				0x2	Analog Comparator 1
				0x3	Reserved
				0x4	External (GPIO PB4)
				0x5	Timer
					In addition, the trigger must be enabled with the ${\tt TnOTE}$ bit in the <b>GPTMCTL</b> register (see page 314).
				0x6	reserved
				0x7	reserved
				8x0	reserved
				0x9-0xE	reserved
				0xF	Always (continuously sample)

# Register 7: ADC Underflow Status (ADCUSTAT), offset 0x018

This register indicates underflow conditions in the sample sequencer FIFOs. The corresponding underflow condition is cleared by writing a 1 to the relevant bit position.

#### ADC Underflow Status (ADCUSTAT)

Base 0x4003.8000 Offset 0x018 Type R/W1C, reset 0x0000.0000



Bit/Field	Name	Туре	Reset	Description
31:4	reserved	RO	0x0000.000	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
3	UV3	R/W1C	0	SS3 FIFO Underflow
				When set, this bit specifies that the FIFO for Sample Sequencer 3 has hit an underflow condition where the FIFO is empty and a read was requested. The problematic read does not move the FIFO pointers, and 0s are returned.
				This bit is cleared by writing a 1.
2	UV2	R/W1C	0	SS2 FIFO Underflow
				When set, this bit specifies that the FIFO for Sample Sequencer 2 has hit an underflow condition where the FIFO is empty and a read was requested. The problematic read does not move the FIFO pointers, and 0s are returned.
				This bit is cleared by writing a 1.
1	UV1	R/W1C	0	SS1 FIFO Underflow
				When set, this bit specifies that the FIFO for Sample Sequencer 1 has hit an underflow condition where the FIFO is empty and a read was requested. The problematic read does not move the FIFO pointers, and 0s are returned.
				This bit is cleared by writing a 1.
0	UV0	R/W1C	0	SS0 FIFO Underflow
				When set, this bit specifies that the FIFO for Sample Sequencer 0 has hit an underflow condition where the FIFO is empty and a read was requested. The problematic read does not move the FIFO pointers, and

0s are returned.

This bit is cleared by writing a 1.


#### Register 8: ADC Sample Sequencer Priority (ADCSSPRI), offset 0x020

This register sets the priority for each of the sample sequencers. Out of reset, Sequencer 0 has the highest priority, and Sequencer 3 has the lowest priority. When reconfiguring sequence priorities, each sequence must have a unique priority for the ADC to operate properly.

#### ADC Sample Sequencer Priority (ADCSSPRI)

Base 0x4003.8000

Offset 0x020 Type R/W, reset 0x0000.3210



Bit/Field	Name	Туре	Reset	Description
31:14	reserved	RO	0x0000.0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
13:12	SS3	R/W	0x3	SS3 Priority  This field contains a binary-encoded value that specifies the priority encoding of Sample Sequencer 3. A priority encoding of 0 is highest and 3 is lowest. The priorities assigned to the sequencers must be uniquely mapped. The ADC may not operate properly if two or more fields are equal.
11:10	reserved	RO	0x0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
9:8	SS2	R/W	0x2	SS2 Priority  This field contains a binary-encoded value that specifies the priority encoding of Sample Sequencer 2. A priority encoding of 0 is highest and 3 is lowest. The priorities assigned to the sequencers must be uniquely mapped. The ADC may not operate properly if two or more fields are equal.
7:6	reserved	RO	0x0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
5:4	SS1	R/W	0x1	SS1 Priority  This field contains a binary-encoded value that specifies the priority encoding of Sample Sequencer 1. A priority encoding of 0 is highest and 3 is lowest. The priorities assigned to the sequencers must be uniquely mapped. The ADC may not operate properly if two or more fields are equal.
3:2	reserved	RO	0x0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.

Bit/Field	Name	Type	Reset	Description
1:0	SS0	R/W	0x0	SS0 Priority  This field contains a binary-encoded value that specifies the priority encoding of Sample Sequencer 0. A priority encoding of 0 is highest and 3 is lowest. The priorities assigned to the sequencers must be uniquely mapped. The ADC may not operate properly if two or more fields are equal.


November 18, 2011 377

#### Register 9: ADC Processor Sample Sequence Initiate (ADCPSSI), offset 0x028

This register provides a mechanism for application software to initiate sampling in the sample sequencers. Sample sequences can be initiated individually or in any combination. When multiple sequences are triggered simultaneously, the priority encodings in **ADCSSPRI** dictate execution order.

ADC Processor Sample Sequence Initiate (ADCPSSI)

Base 0x4003.8000 Offset 0x028 Type WO, reset -



Bit/Field	Name	Туре	Reset	Description
31:4	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
3	SS3	WO	-	SS3 Initiate
				When set, this bit triggers sampling on Sample Sequencer 3 if the sequencer is enabled in the <b>ADCACTSS</b> register.
				Only a write by software is valid; a read of this register returns no meaningful data.
2	SS2	WO	_	SS2 Initiate
				When set, this bit triggers sampling on Sample Sequencer 2 if the sequencer is enabled in the <b>ADCACTSS</b> register.
				Only a write by software is valid; a read of this register returns no meaningful data.
1	SS1	WO	-	SS1 Initiate
				When set, this bit triggers sampling on Sample Sequencer 1 if the sequencer is enabled in the <b>ADCACTSS</b> register.
				Only a write by software is valid; a read of this register returns no meaningful data.
0	SS0	WO	-	SS0 Initiate
				When set, this bit triggers sampling on Sample Sequencer 0 if the sequencer is enabled in the <b>ADCACTSS</b> register.
				Only a write by software is valid; a read of this register returns no


meaningful data.

# Register 10: ADC Sample Averaging Control (ADCSAC), offset 0x030

This register controls the amount of hardware averaging applied to conversion results. The final conversion result stored in the FIFO is averaged from  $2^{\text{AVG}}$  consecutive ADC samples at the specified ADC speed. If AVG is 0, the sample is passed directly through without any averaging. If AVG=6, then 64 consecutive ADC samples are averaged to generate one result in the sequencer FIFO. An AVG = 7 provides unpredictable results.

#### ADC Sample Averaging Control (ADCSAC)

Base 0x4003.8000 Offset 0x030 Type R/W, reset 0x0000.0000



Bit/Field	Name	Type	Reset	Description
31:3	reserved	RO	0x0000.000	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
2:0	AVG	R/W	0x0	Hardware Averaging Control

Specifies the amount of hardware averaging that will be applied to ADC samples. The AVG field can be any value between 0 and 6. Entering a value of 7 creates unpredictable results.

Value Description 0x0 No hardware oversampling 2x hardware oversampling 0x1 0x2 4x hardware oversampling 0x3 8x hardware oversampling 16x hardware oversampling 0x4 32x hardware oversampling 0x5 64x hardware oversampling 0x6 0x7 Reserved

## Register 11: ADC Sample Sequence Input Multiplexer Select 0 (ADCSSMUX0), offset 0x040

This register defines the analog input configuration for each sample in a sequence executed with Sample Sequencer 0. This register is 32 bits wide and contains information for eight possible samples.

ADC Sample Sequence Input Multiplexer Select 0 (ADCSSMUX0)

Base 0x4003.8000 Offset 0x040 Type R/W, reset 0x0000.0000

	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16
		reserved		MUX7		reserved	•	MUX6		reserved		MUX5		reserved		MUX4
Туре	RO	RO	RO	R/W	RO	RO	RO	R/W	RO	RO	RO	R/W	RO	RO	RO	R/W
Reset	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0
	15	14	13	12	11	10	9	8	7	6	5	4	3	2	1	0
		reserved		MUX3		reserved	'	MUX2		reserved		MUX1		reserved		MUX0
Туре	RO 0	RO 0	RO 0	R/W 0	RO 0	RO 0	RO 0	R/W 0	RO 0	RO 0	RO 0	R/W 0	RO 0	RO	RO 0	R/W
Reset	U	U	U	U	U	U	U	U	U	U	U	U	U	0	U	0
E	Bit/Field		Nan	ne	Ту	ре	Reset	Des	cription							
	31:29		reser	hav	D	.O	0	Soft	wara ch	ould not r	alv on t	he value	of a res	served bit.	To prov	vide
	31.29		10301	veu	1	.0	O	com	patibility		re prod	ucts, the	value o	f a reserve	•	
	28		MUX	<b>X</b> 7	R	W	0x0	8th	Sample	Input Sele	ect					
												the eight	h sampl	le of a sequ	uence e	executed
														of the and		
														he value se of 1 indicat		
								ADC		oriding pin	i, ioi ex	атріс, а	value C	n i ilidicat	.cs tric	Tiput is
	27:25		reser	ved	D	0	0	Soft	ware ch	ould not r	elv on t	he value	of a rec	served bit.	To prov	vide
	21.23		16361	veu	IN	.0	U							f a reserve		
								pres	served a	cross a re	ad-mo	dify-write	operati	on.		
	24		MUX	X6	R	W	0x0	7th	Sample	Input Sele	ect					
								The	MUX6 fi	eld is use	d durin	g the sev	enth sa	mple of a	sequen	ce
												•		ifies which	of the	analog
								inpu	its is sai	mpled for	tne ana	liog-to-ai	gitai cor	iversion.		
	23:21		reser	ved	R	.0	0				-			served bit.		
										/ with futu cross a re	•			f a reserve	ed bit sh	nould be
												uyc	opo.aa	···		
	20		MUX	<b>X</b> 5	R	W	0x0			Input Sele				_		
														e of a sequal of the ana		
										the analo				. 5	~cgt	
	19:17		reser	ved		0	0	S∨#	waro sh	ould not r	alv on t	he value	of a roc	served bit.	To prov	vide
	19.17		16961	v <del>c</del> u	K	.0	U							f a reserve		
										cross a re	•					

Bit/Field	Name	Туре	Reset	Description
16	MUX4	R/W	0x0	5th Sample Input Select The $\texttt{MUX4}$ field is used during the fifth sample of a sequence executed with the sample sequencer. It specifies which of the analog inputs is sampled for the analog-to-digital conversion.
15:13	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
12	MUX3	R/W	0x0	4th Sample Input Select The MUX3 field is used during the fourth sample of a sequence executed with the sample sequencer. It specifies which of the analog inputs is sampled for the analog-to-digital conversion.
11:9	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
8	MUX2	R/W	0x0	3rd Sample Input Select The MUX72 field is used during the third sample of a sequence executed with the sample sequencer. It specifies which of the analog inputs is sampled for the analog-to-digital conversion.
7:5	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
4	MUX1	R/W	0x0	2nd Sample Input Select The MUX1 field is used during the second sample of a sequence executed with the sample sequencer. It specifies which of the analog inputs is sampled for the analog-to-digital conversion.
3:1	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
0	MUX0	R/W	0x0	1st Sample Input Select The MUX0 field is used during the first sample of a sequence executed with the sample sequencer. It specifies which of the analog inputs is sampled for the analog-to-digital conversion.

# Register 12: ADC Sample Sequence Control 0 (ADCSSCTL0), offset 0x044

This register contains the configuration information for each sample for a sequence executed with a sample sequencer. When configuring a sample sequence, the END bit must be set at some point, whether it be after the first sample, last sample, or any sample in between. This register is 32-bits wide and contains information for eight possible samples.

#### ADC Sample Sequence Control 0 (ADCSSCTL0)

Base 0x4003.8000

Offset 0x044 Type R/W, reset 0x0000.0000

	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16
	TS7	IE7	END7	D7	TS6	IE6	END6	D6	TS5	IE5	END5	D5	TS4	IE4	END4	D4
Туре	R/W	R/W	R/W	R/W	R/W	R/W	R/W	R/W	R/W	R/W	R/W	R/W	R/W	R/W	R/W	R/W
Reset	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0
	15	14	13	12	11	10	9	8	7	6	5	4	3	2	1	0
•	15 TS3	14 IE3	13 END3	12 D3	11 TS2	10 IE2	9 END2	8 D2	7 TS1	6 IE1	5 END1	4 D1	3 TS0	2 IE0	1 END0	0 D0

Bit/Field	Name	Туре	Reset	Description
31	TS7	R/W	0	8th Sample Temp Sensor Select
				This bit is used during the eighth sample of the sample sequence and and specifies the input source of the sample.
				When set, the temperature sensor is read.
				When clear, the input pin specified by the <b>ADCSSMUX</b> register is read.
30	IE7	R/W	0	8th Sample Interrupt Enable
				This bit is used during the eighth sample of the sample sequence and specifies whether the raw interrupt signal (INRO bit) is asserted at the end of the sample's conversion. If the MASKO bit in the <b>ADCIM</b> register is set, the interrupt is promoted to a controller-level interrupt.
				When this bit is set, the raw interrupt is asserted.
				When this bit is clear, the raw interrupt is not asserted.
				It is legal to have multiple samples within a sequence generate interrupts.
29	END7	R/W	0	8th Sample is End of Sequence
				The END7 bit indicates that this is the last sample of the sequence. It is possible to end the sequence on any sample position. Samples defined after the sample containing a set END are not requested for conversion even though the fields may be non-zero. It is required that software write the END bit somewhere within the sequence. (Sample Sequencer 3, which only has a single sample in the sequence, is hardwired to have the END0 bit set.)
				Setting this bit indicates that this sample is the last in the sequence.
28	D7	R/W	0	8th Sample Diff Input Select
				The D7 bit indicates that the analog input is to be differentially sampled. The corresponding <b>ADCSSMUXx</b> nibble must be set to the pair number "i", where the paired inputs are "2i and 2i+1". The temperature sensor does not have a differential option. When set, the analog inputs are differentially sampled.
27	TS6	R/W	0	7th Sample Temp Sensor Select
				Same definition as TS7 but used during the seventh sample.

Bit/Field	Name	Туре	Reset	Description
26	IE6	R/W	0	7th Sample Interrupt Enable Same definition as IE7 but used during the seventh sample.
25	END6	R/W	0	7th Sample is End of Sequence Same definition as END7 but used during the seventh sample.
24	D6	R/W	0	7th Sample Diff Input Select Same definition as D7 but used during the seventh sample.
23	TS5	R/W	0	6th Sample Temp Sensor Select Same definition as TS7 but used during the sixth sample.
22	IE5	R/W	0	6th Sample Interrupt Enable Same definition as IE7 but used during the sixth sample.
21	END5	R/W	0	6th Sample is End of Sequence Same definition as END7 but used during the sixth sample.
20	D5	R/W	0	6th Sample Diff Input Select Same definition as D7 but used during the sixth sample.
19	TS4	R/W	0	5th Sample Temp Sensor Select Same definition as TS7 but used during the fifth sample.
18	IE4	R/W	0	5th Sample Interrupt Enable Same definition as IE7 but used during the fifth sample.
17	END4	R/W	0	5th Sample is End of Sequence Same definition as END7 but used during the fifth sample.
16	D4	R/W	0	5th Sample Diff Input Select Same definition as D7 but used during the fifth sample.
15	TS3	R/W	0	4th Sample Temp Sensor Select Same definition as TS7 but used during the fourth sample.
14	IE3	R/W	0	4th Sample Interrupt Enable Same definition as IE7 but used during the fourth sample.
13	END3	R/W	0	4th Sample is End of Sequence Same definition as END7 but used during the fourth sample.
12	D3	R/W	0	4th Sample Diff Input Select Same definition as D7 but used during the fourth sample.
11	TS2	R/W	0	3rd Sample Temp Sensor Select Same definition as TS7 but used during the third sample.
10	IE2	R/W	0	3rd Sample Interrupt Enable Same definition as IE7 but used during the third sample.
9	END2	R/W	0	3rd Sample is End of Sequence Same definition as END7 but used during the third sample.

Bit/Field	Name	Type	Reset	Description
8	D2	R/W	0	3rd Sample Diff Input Select Same definition as D7 but used during the third sample.
7	TS1	R/W	0	2nd Sample Temp Sensor Select Same definition as TS7 but used during the second sample.
6	IE1	R/W	0	2nd Sample Interrupt Enable Same definition as IE7 but used during the second sample.
5	END1	R/W	0	2nd Sample is End of Sequence Same definition as END7 but used during the second sample.
4	D1	R/W	0	2nd Sample Diff Input Select Same definition as D7 but used during the second sample.
3	TS0	R/W	0	1st Sample Temp Sensor Select Same definition as TS7 but used during the first sample.
2	IE0	R/W	0	1st Sample Interrupt Enable Same definition as IE7 but used during the first sample.
1	END0	R/W	0	1st Sample is End of Sequence Same definition as END7 but used during the first sample.
0	D0	R/W	0	1st Sample Diff Input Select Same definition as D7 but used during the first sample.


Register 13: ADC Sample Sequence Result FIFO 0 (ADCSSFIFO0), offset 0x048 Register 14: ADC Sample Sequence Result FIFO 1 (ADCSSFIFO1), offset 0x068 Register 15: ADC Sample Sequence Result FIFO 2 (ADCSSFIFO2), offset 0x088 Register 16: ADC Sample Sequence Result FIFO 3 (ADCSSFIFO3), offset 0x0A8

**Important:** This register is read-sensitive. See the register description for details.

This register contains the conversion results for samples collected with the sample sequencer (the ADCSSFIFO0 register is used for Sample Sequencer 0, ADCSSFIFO1 for Sequencer 1, ADCSSFIFO2 for Sequencer 2, and ADCSSFIFO3 for Sequencer 3). Reads of this register return conversion result data in the order sample 0, sample 1, and so on, until the FIFO is empty. If the FIFO is not properly handled by software, overflow and underflow conditions are registered in the ADCOSTAT and ADCUSTAT registers.

#### ADC Sample Sequence Result FIFO 0 (ADCSSFIFO0)

Base 0x4003.8000 Offset 0x048 Type RO, reset -



Bit/Field	Name	Type	Reset	Description
31:10	reserved	RO	-	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
9:0	DATA	RO	-	Conversion Result Data

Register 17: ADC Sample Sequence FIFO 0 Status (ADCSSFSTAT0), offset 0x04C

Register 18: ADC Sample Sequence FIFO 1 Status (ADCSSFSTAT1), offset 0x06C

Register 19: ADC Sample Sequence FIFO 2 Status (ADCSSFSTAT2), offset 0x08C

# Register 20: ADC Sample Sequence FIFO 3 Status (ADCSSFSTAT3), offset 0x0AC

This register provides a window into the sample sequencer, providing full/empty status information as well as the positions of the head and tail pointers. The reset value of 0x100 indicates an empty FIFO. The ADCSSFSTAT0 register provides status on FIFO0, ADCSSFSTAT1 on FIFO1, ADCSSFSTAT2 on FIFO2, and ADCSSFSTAT3 on FIFO3.

#### ADC Sample Sequence FIFO 0 Status (ADCSSFSTAT0)

Base 0x4003.8000 Offset 0x04C Type RO, reset 0x0000.0100

_	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16
						1		rese	rved							
Type	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO
Туре					KU	KU		RO	KO.	KU			RO	KU	RO	
Reset	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0
_	15	14	13	12	11	10	9	8	7	6	5	4	3	2	1	0
ſ		reserved		FULL		reserved		EMPTY		HP	TR			TP	TR	
Type <sup>1</sup>	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO
Reset	0	0	0	0	0	0	0	1	0	0	0	0	0	0	0	0

Bit/Field	Name	Туре	Reset	Description
31:13	reserved	RO	0x0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
12	FULL	RO	0	FIFO Full
				When set, this bit indicates that the FIFO is currently full.
11:9	reserved	RO	0x0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
8	EMPTY	RO	1	FIFO Empty
				When set, this bit indicates that the FIFO is currently empty.
7:4	HPTR	RO	0x0	FIFO Head Pointer
				This field contains the current "head" pointer index for the FIFO, that is, the next entry to be written.
3:0	TPTR	RO	0x0	FIFO Tail Pointer
				This field contains the current "tail" pointer index for the FIFO, that is, the next entry to be read.

# Register 21: ADC Sample Sequence Input Multiplexer Select 1 (ADCSSMUX1), offset 0x060


# Register 22: ADC Sample Sequence Input Multiplexer Select 2 (ADCSSMUX2), offset 0x080

This register defines the analog input configuration for each sample in a sequence executed with Sample Sequencer 1 or 2. These registers are 16-bits wide and contain information for four possible samples. See the **ADCSSMUX0** register on page 380 for detailed bit descriptions. The **ADCSSMUX1** register affects Sample Sequencer 1 and the **ADCSSMUX2** register affects Sample Sequencer 2.

ADC Sample Sequence Input Multiplexer Select 1 (ADCSSMUX1)

Base 0x4003.8000 Offset 0x060

Type R/W, reset 0x0000.0000



Bit/Field	Name	Туре	Reset	Description
31:13	reserved	RO	0x0000	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
12	MUX3	R/W	0x0	4th Sample Input Select
11:9	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
8	MUX2	R/W	0x0	3rd Sample Input Select
7:5	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
4	MUX1	R/W	0x0	2nd Sample Input Select
3:1	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
0	MUX0	R/W	0x0	1st Sample Input Select

# Register 23: ADC Sample Sequence Control 1 (ADCSSCTL1), offset 0x064 Register 24: ADC Sample Sequence Control 2 (ADCSSCTL2), offset 0x084

These registers contain the configuration information for each sample for a sequence executed with Sample Sequencer 1 or 2. When configuring a sample sequence, the END bit must be set at some point, whether it be after the first sample, last sample, or any sample in between. These registers are 16-bits wide and contain information for four possible samples. See the **ADCSSCTL0** register on page 382 for detailed bit descriptions. The **ADCSSCTL1** register configures Sample Sequencer 1 and the **ADCSSCTL2** register configures Sample Sequencer 2.

#### ADC Sample Sequence Control 1 (ADCSSCTL1)

Base 0x4003.8000 Offset 0x064

Type R/W, reset 0x0000.0000

	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16
			•					rese	rved •				l I	'		
Type Reset	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0
	15	14	13	12	11	10	9	8	7	6	5	4	3	2	1	0
	TS3	IE3	END3	D3	TS2	IE2	END2	D2	TS1	IE1	END1	D1	TS0	IE0	END0	D0
Type Reset	R/W 0	R/W 0	R/W 0	R/W 0	R/W 0	R/W 0	R/W 0	R/W 0	R/W 0	R/W 0	R/W 0	R/W 0	R/W 0	R/W 0	R/W 0	R/W 0
Е	sit/Field		Nam	ne	Ту	ре	Reset	Des	cription							
	31:16		reserv	/ed	R	0	0x0000	com		with futu	ure produ	ucts, the	value of	a reserv	To prov red bit sh	
	15		TS	3	R/	W	0		Sample ine definit	•			ng the fo	ourth san	nple.	
	14		IE3	3	R/	W	0		Sample ne definit	•		sed duri	ng the fo	ourth san	nple.	
	13		END	03	R/	W	0		Sample ine definit				ring the t	fourth sa	mple.	
	12		D3	i	R/	W	0		Sample l	•		ed durin	g the fou	rth samp	ole.	
	11		TS2	2	R/	W	0		Sample ne definit				ng the th	ird samp	ole.	
	10		IE2	2	R/	W	0		Sample ne definit	•		sed duri	ng the th	ird samp	ole.	
	9		END	)2	R/	W	0		Sample ne definit				ring the t	third san	nple.	
	8		D2		R/	W	0		Sample ne definit			ed durin	g the thir	d sample	е.	
	7		TS	1	R/	W	0	2nd	Sample	Temp Se	ensor Se	elect				

Same definition as TS7 but used during the second sample.

Bit/Field	Name	Туре	Reset	Description
6	IE1	R/W	0	2nd Sample Interrupt Enable Same definition as IE7 but used during the second sample.
5	END1	R/W	0	2nd Sample is End of Sequence Same definition as END7 but used during the second sample.
4	D1	R/W	0	2nd Sample Diff Input Select Same definition as D7 but used during the second sample.
3	TS0	R/W	0	1st Sample Temp Sensor Select Same definition as TS7 but used during the first sample.
2	IE0	R/W	0	1st Sample Interrupt Enable Same definition as IE7 but used during the first sample.
1	END0	R/W	0	1st Sample is End of Sequence Same definition as END7 but used during the first sample.
0	D0	R/W	0	1st Sample Diff Input Select Same definition as D7 but used during the first sample.


## Register 25: ADC Sample Sequence Input Multiplexer Select 3 (ADCSSMUX3), offset 0x0A0

This register defines the analog input configuration for a sample executed with Sample Sequencer 3. This register is 4-bits wide and contains information for one possible sample. See the ADCSSMUX0 register on page 380 for detailed bit descriptions.

ADC Sample Sequence Input Multiplexer Select 3 (ADCSSMUX3)

Base 0x4003.8000

Offset 0x0A0
Type R/W, reset 0x0000.0000



Bit/Field	Name	Type	Reset	Description
31:1	reserved	RO	0x0000.000	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
0	MUX0	R/W	0	1st Sample Input Select


# Register 26: ADC Sample Sequence Control 3 (ADCSSCTL3), offset 0x0A4

This register contains the configuration information for a sample executed with Sample Sequencer 3. The END bit is always set since there is only one sample in this sequencer. This register is 4-bits wide and contains information for one possible sample. See the **ADCSSCTL0** register on page 382 for detailed bit descriptions.

#### ADC Sample Sequence Control 3 (ADCSSCTL3)

Base 0x4003.8000 Offset 0x0A4

Type R/W, reset 0x0000.0002



Bit/Field	Name	Туре	Reset	Description
31:4	reserved	RO	0x0000.000	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
3	TS0	R/W	0	1st Sample Temp Sensor Select Same definition as TS7 but used during the first sample.
2	IE0	R/W	0	1st Sample Interrupt Enable Same definition as IE7 but used during the first sample.
1	END0	R/W	1	1st Sample is End of Sequence Same definition as END7 but used during the first sample. Since this sequencer has only one entry, this bit must be set.
0	D0	R/W	0	1st Sample Diff Input Select Same definition as D7 but used during the first sample.


# Register 27: ADC Test Mode Loopback (ADCTMLB), offset 0x100

This register provides loopback operation within the digital logic of the ADC, which can be useful in debugging software without having to provide actual analog stimulus. This test mode is entered by writing a value of 0x0000.0001 to this register. When data is read from the FIFO in loopback mode, the read-only portion of this register is returned.

#### ADC Test Mode Loopback (ADCTMLB)

Base 0x4003.8000

Offset 0x100 Type R/W, reset 0x0000.0000



Bit/Field	Name	Туре	Reset	Description
31:1	reserved	RO	0x0000.000	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
0	I R	R/W	0	Loonback Mode Enable

When set, forces a loopback within the digital block to provide information on input and unique numbering. The ADCSSFIFOn registers do not provide sample data, but instead provide the 10-bit loopback data as shown below.

Bit/Field Name	Description
9:6 CNT	Continuous Sample Counter
	Continuous sample counter that is initialized to 0 and counts each sample as it processed. This helps provide a unique value for the data received.
5 CON	Continuation Sample Indicator
	When set, indicates that this is a continuation sample. For example, if two sequencers were to run back-to-back, this indicates that the controller kept continuously sampling at full rate.
4 DIFF	Differential Sample Indicator
	When set, indicates that this is a differential sample.
3 TS	Temp Sensor Sample Indicator
	When set, indicates that this is a temperature sensor sample.
2:0 MUX	Analog Input Indicator
	Indicates which analog input is to be sampled.

# 11 Universal Asynchronous Receivers/Transmitters (UARTs)

The Stellaris<sup>®</sup> Universal Asynchronous Receiver/Transmitter (UART) has the following features:

- Fully programmable 16C550-type UART with IrDA support
- Separate 16x8 transmit (TX) and receive (RX) FIFOs to reduce CPU interrupt service loading
- Programmable baud-rate generator allowing speeds up to 1.5625 Mbps
- Programmable FIFO length, including 1-byte deep operation providing conventional double-buffered interface
- FIFO trigger levels of 1/8, 1/4, 1/2, 3/4, and 7/8
- Standard asynchronous communication bits for start, stop, and parity
- Line-break generation and detection
- Fully programmable serial interface characteristics
  - 5, 6, 7, or 8 data bits
  - Even, odd, stick, or no-parity bit generation/detection
  - 1 or 2 stop bit generation
- IrDA serial-IR (SIR) encoder/decoder providing
  - Programmable use of IrDA Serial Infrared (SIR) or UART input/output
  - Support of IrDA SIR encoder/decoder functions for data rates up to 115.2 Kbps half-duplex
  - Support of normal 3/16 and low-power (1.41-2.23 μs) bit durations
  - Programmable internal clock generator enabling division of reference clock by 1 to 256 for low-power mode bit duration

# 11.1 Block Diagram

Figure 11-1. UART Module Block Diagram

System Clock Interrupt **TxFIFO Interrupt Control** 16 x 8 **UARTIFLS UARTIM UARTMIS** Identification UARTRIS Registers **UARTICR** Transmitter UARTPCellID0 UnTx (with SIR UARTPCellID1 Transmit **Baud Rate** UARTPCellID2 Encoder) Generator UARTPCellID3 **UARTDR** UARTPeriphID0 **UARTIBRD** UARTPeriphID1 UARTFBRD Receiver UnRx UARTPeriphID2 (with SIR UARTPeriphID3 Receive UARTPeriphID4 Decoder) **RxFIFO** Control/Status UARTPeriphID5 16 x 8 UARTPeriphID6 UARTPeriphID7 UARTRSR/ECR **UARTFR** UARTLCRH UARTCTL **UARTILPR** 

# 11.2 Signal Description

Table 11-1 on page 394 and Table 11-2 on page 395 list the external signals of the UART module and describe the function of each. The UART signals are alternate functions for some GPIO signals and default to be GPIO signals at reset, with the exception of the  $\mathtt{UORx}$  and  $\mathtt{UOTx}$  pins which default to the UART function. The column in the table below titled "Pin Assignment" lists the possible GPIO pin placements for these UART signals. The AFSEL bit in the **GPIO Alternate Function Select (GPIOAFSEL)** register (page 272) should be set to choose the UART function. For more information on configuring GPIOs, see "General-Purpose Input/Outputs (GPIOs)" on page 251.

Table 11-1. UART Signals (100LQFP)

Pin Name	Pin Number	Pin Type	Buffer Type <sup>a</sup>	Description
U0Rx	26	I		UART module 0 receive. When in IrDA mode, this signal has IrDA modulation.
UOTx	27	0		UART module 0 transmit. When in IrDA mode, this signal has IrDA modulation.

a. The TTL designation indicates the pin has TTL-compatible voltage levels.

Table 11-2. UART Signals (108BGA)

Pin Name	Pin Number	Pin Type	Buffer Type <sup>a</sup>	Description
U0Rx	L3	I	TTL	UART module 0 receive. When in IrDA mode, this signal has IrDA modulation.
UOTx	M3	0		UART module 0 transmit. When in IrDA mode, this signal has IrDA modulation.

a. The TTL designation indicates the pin has TTL-compatible voltage levels.

# 11.3 Functional Description

Each Stellaris UART performs the functions of parallel-to-serial and serial-to-parallel conversions. It is similar in functionality to a 16C550 UART, but is not register compatible.

The UART is configured for transmit and/or receive via the TXE and RXE bits of the **UART Control** (**UARTCTL**) register (see page 413). Transmit and receive are both enabled out of reset. Before any control registers are programmed, the UART must be disabled by clearing the UARTEN bit in **UARTCTL**. If the UART is disabled during a TX or RX operation, the current transaction is completed prior to the UART stopping.


The UART peripheral also includes a serial IR (SIR) encoder/decoder block that can be connected to an infrared transceiver to implement an IrDA SIR physical layer. The SIR function is programmed using the UARTCTL register.

### 11.3.1 Transmit/Receive Logic

The transmit logic performs parallel-to-serial conversion on the data read from the transmit FIFO. The control logic outputs the serial bit stream beginning with a start bit, and followed by the data bits (LSB first), parity bit, and the stop bits according to the programmed configuration in the control registers. See Figure 11-2 on page 395 for details.

The receive logic performs serial-to-parallel conversion on the received bit stream after a valid start pulse has been detected. Overrun, parity, frame error checking, and line-break detection are also performed, and their status accompanies the data that is written to the receive FIFO.

Figure 11-2. UART Character Frame



#### 11.3.2 Baud-Rate Generation

The baud-rate divisor is a 22-bit number consisting of a 16-bit integer and a 6-bit fractional part. The number formed by these two values is used by the baud-rate generator to determine the bit period. Having a fractional baud-rate divider allows the UART to generate all the standard baud rates.

The 16-bit integer is loaded through the **UART Integer Baud-Rate Divisor (UARTIBRD)** register (see page 409) and the 6-bit fractional part is loaded with the **UART Fractional Baud-Rate Divisor (UARTFBRD)** register (see page 410). The baud-rate divisor (BRD) has the following relationship to the system clock (where *BRDI* is the integer part of the *BRD* and *BRDF* is the fractional part, separated by a decimal place.)

```
BRD = BRDI + BRDF = UARTSysClk / (16 * Baud Rate)
```

where <code>UARTSysClk</code> is the system clock connected to the UART.

The 6-bit fractional number (that is to be loaded into the DIVFRAC bit field in the **UARTFBRD** register) can be calculated by taking the fractional part of the baud-rate divisor, multiplying it by 64, and adding 0.5 to account for rounding errors:

```
UARTFBRD[DIVFRAC] = integer(BRDF * 64 + 0.5)
```

The UART generates an internal baud-rate reference clock at 16x the baud-rate (referred to as Baud16). This reference clock is divided by 16 to generate the transmit clock, and is used for error detection during receive operations.

Along with the **UART Line Control**, **High Byte (UARTLCRH)** register (see page 411), the **UARTIBRD** and **UARTFBRD** registers form an internal 30-bit register. This internal register is only updated when a write operation to **UARTLCRH** is performed, so any changes to the baud-rate divisor must be followed by a write to the **UARTLCRH** register for the changes to take effect.

To update the baud-rate registers, there are four possible sequences:

- UARTIBRD write, UARTFBRD write, and UARTLCRH write
- UARTFBRD write, UARTIBRD write, and UARTLCRH write
- UARTIBRD write and UARTLCRH write
- UARTFBRD write and UARTLCRH write

#### 11.3.3 Data Transmission

Data received or transmitted is stored in two 16-byte FIFOs, though the receive FIFO has an extra four bits per character for status information. For transmission, data is written into the transmit FIFO. If the UART is enabled, it causes a data frame to start transmitting with the parameters indicated in the **UARTLCRH** register. Data continues to be transmitted until there is no data left in the transmit FIFO. The BUSY bit in the **UART Flag (UARTFR)** register (see page 406) is asserted as soon as data is written to the transmit FIFO (that is, if the FIFO is non-empty) and remains asserted while data is being transmitted. The BUSY bit is negated only when the transmit FIFO is empty, and the last character has been transmitted from the shift register, including the stop bits. The UART can indicate that it is busy even though the UART may no longer be enabled.

When the receiver is idle (the UnRx is continuously 1) and the data input goes Low (a start bit has been received), the receive counter begins running and data is sampled on the eighth cycle of Baud16 (described in "Transmit/Receive Logic" on page 395).

The start bit is valid and recognized if UnRx is still low on the eighth cycle of Baud16, otherwise it is ignored. After a valid start bit is detected, successive data bits are sampled on every 16th cycle of Baud16 (that is, one bit period later) according to the programmed length of the data characters. The parity bit is then checked if parity mode was enabled. Data length and parity are defined in the **UARTLCRH** register.

Lastly, a valid stop bit is confirmed if UnRx is High, otherwise a framing error has occurred. When a full word is received, the data is stored in the receive FIFO, with any error bits associated with that word.

#### 11.3.4 **Serial IR (SIR)**

The UART peripheral includes an IrDA serial-IR (SIR) encoder/decoder block. The IrDA SIR block provides functionality that converts between an asynchronous UART data stream, and half-duplex serial SIR interface. No analog processing is performed on-chip. The role of the SIR block is to provide a digital encoded output and decoded input to the UART. The UART signal pins can be connected to an infrared transceiver to implement an IrDA SIR physical layer link. The SIR block has two modes of operation:

- In normal IrDA mode, a zero logic level is transmitted as high pulse of 3/16th duration of the selected baud rate bit period on the output pin, while logic one levels are transmitted as a static LOW signal. These levels control the driver of an infrared transmitter, sending a pulse of light for each zero. On the reception side, the incoming light pulses energize the photo transistor base of the receiver, pulling its output LOW. This drives the UART input pin LOW.
- In low-power IrDA mode, the width of the transmitted infrared pulse is set to three times the period of the internally generated IrLPBaud16 signal (1.63 μs, assuming a nominal 1.8432 MHz frequency) by changing the appropriate bit in the UARTCR register. See page 408 for more information on IrDA low-power pulse-duration configuration.

Figure 11-3 on page 397 shows the UART transmit and receive signals, with and without IrDA modulation.




Figure 11-3. IrDA Data Modulation

In both normal and low-power IrDA modes:

- During transmission, the UART data bit is used as the base for encoding
- During reception, the decoded bits are transferred to the UART receive logic

The IrDA SIR physical layer specifies a half-duplex communication link, with a minimum 10 ms delay between transmission and reception. This delay must be generated by software because it is not automatically supported by the UART. The delay is required because the infrared receiver electronics might become biased, or even saturated from the optical power coupled from the adjacent transmitter LED. This delay is known as latency, or receiver setup time.

If the application does not require the use of the  $\mathtt{UnRx}$  signal, the GPIO pin that has the  $\mathtt{UnRx}$  signal as an alternate function must be configured as the  $\mathtt{UnRx}$  signal and pulled High.

#### 11.3.5 FIFO Operation

The UART has two 16-entry FIFOs; one for transmit and one for receive. Both FIFOs are accessed via the **UART Data (UARTDR)** register (see page 402). Read operations of the **UARTDR** register return a 12-bit value consisting of 8 data bits and 4 error flags while write operations place 8-bit data in the transmit FIFO.

Out of reset, both FIFOs are disabled and act as 1-byte-deep holding registers. The FIFOs are enabled by setting the FEN bit in **UARTLCRH** (page 411).

FIFO status can be monitored via the **UART Flag (UARTFR)** register (see page 406) and the **UART Receive Status (UARTRSR)** register. Hardware monitors empty, full and overrun conditions. The **UARTFR** register contains empty and full flags (TXFE, TXFF, RXFE, and RXFF bits) and the **UARTRSR** register shows overrun status via the OE bit.

The trigger points at which the FIFOs generate interrupts is controlled via the **UART Interrupt FIFO Level Select (UARTIFLS)** register (see page 415). Both FIFOs can be individually configured to trigger interrupts at different levels. Available configurations include 1/8, ½, ½, ¾, and 7/8. For example, if the ¼ option is selected for the receive FIFO, the UART generates a receive interrupt after 4 data bytes are received. Out of reset, both FIFOs are configured to trigger an interrupt at the ½ mark.

#### 11.3.6 Interrupts

The UART can generate interrupts when the following conditions are observed:

- Overrun Error
- Break Error
- Parity Error
- Framing Error
- Receive Timeout
- Transmit (when condition defined in the TXIFLSEL bit in the UARTIFLS register is met)
- Receive (when condition defined in the RXIFLSEL bit in the **UARTIFLS** register is met)

All of the interrupt events are ORed together before being sent to the interrupt controller, so the UART can only generate a single interrupt request to the controller at any given time. Software can service multiple interrupt events in a single interrupt service routine by reading the **UART Masked Interrupt Status (UARTMIS)** register (see page 420).

The interrupt events that can trigger a controller-level interrupt are defined in the **UART Interrupt Mask (UARTIM**) register (see page 417) by setting the corresponding IM bit to 1. If interrupts are not used, the raw interrupt status is always visible via the **UART Raw Interrupt Status (UARTRIS)** register (see page 419).

Interrupts are always cleared (for both the **UARTMIS** and **UARTRIS** registers) by setting the corresponding bit in the **UART Interrupt Clear (UARTICR)** register (see page 421).

The receive interrupt changes state when one of the following events occurs:

- If the FIFOs are enabled and the receive FIFO reaches the programmed trigger level, the RXRIS bit is set. The receive interrupt is cleared by reading data from the receive FIFO until it becomes less than the trigger level, or by clearing the interrupt by writing a 1 to the RXIC bit.
- If the FIFOs are disabled (have a depth of one location) and data is received thereby filling the location, the RXRIS bit is set. The receive interrupt is cleared by performing a single read of the receive FIFO, or by clearing the interrupt by writing a 1 to the RXIC bit.

The transmit interrupt changes state when one of the following events occurs:

- If the FIFOs are enabled and the transmit FIFO reaches the programmed trigger level, the TXRIS bit is set. The transmit interrupt is cleared by writing data to the transmit FIFO until it becomes greater than the trigger level, or by clearing the interrupt by writing a 1 to the TXIC bit.
- If the FIFOs are disabled (have a depth of one location) and there is no data present in the transmitters single location, the TXRIS bit is set. It is cleared by performing a single write to the transmit FIFO, or by clearing the interrupt by writing a 1 to the TXIC bit.

#### 11.3.7 Loopback Operation

The UART can be placed into an internal loopback mode for diagnostic or debug work. This is accomplished by setting the LBE bit in the **UARTCTL** register (see page 413). In loopback mode, data transmitted on UnTx is received on the UnRx input.

#### 11.3.8 IrDA SIR block

The IrDA SIR block contains an IrDA serial IR (SIR) protocol encoder/decoder. When enabled, the SIR block uses the  $\mathtt{UnTx}$  and  $\mathtt{UnRx}$  pins for the SIR protocol, which should be connected to an IR transceiver.

The SIR block can receive and transmit, but it is only half-duplex so it cannot do both at the same time. Transmission must be stopped before data can be received. The IrDA SIR physical layer specifies a minimum 10-ms delay between transmission and reception.

### 11.4 Initialization and Configuration

To use the UART, the peripheral clock must be enabled by setting the UARTO bit in the **RCGC1** register.

This section discusses the steps that are required to use a UART module. For this example, the UART clock is assumed to be 20 MHz and the desired UART configuration is:

- 115200 baud rate
- Data length of 8 bits
- One stop bit
- No parity
- FIFOs disabled
- No interrupts

The first thing to consider when programming the UART is the baud-rate divisor (BRD), since the **UARTIBRD** and **UARTFBRD** registers must be written before the **UARTLCRH** register. Using the equation described in "Baud-Rate Generation" on page 395, the BRD can be calculated:

```
BRD = 20,000,000 / (16 * 115,200) = 10.8507
```

which means that the DIVINT field of the **UARTIBRD** register (see page 409) should be set to 10. The value to be loaded into the **UARTFBRD** register (see page 410) is calculated by the equation:

```
UARTFBRD[DIVFRAC] = integer(0.8507 * 64 + 0.5) = 54
```

With the BRD values in hand, the UART configuration is written to the module in the following order:

- 1. Disable the UART by clearing the UARTEN bit in the **UARTCTL** register.
- 2. Write the integer portion of the BRD to the **UARTIBRD** register.
- Write the fractional portion of the BRD to the UARTFBRD register.
- **4.** Write the desired serial parameters to the **UARTLCRH** register (in this case, a value of 0x0000.0060).
- 5. Enable the UART by setting the UARTEN bit in the **UARTCTL** register.

### 11.5 Register Map

Table 11-3 on page 400 lists the UART registers. The offset listed is a hexadecimal increment to the register's address, relative to that UART's base address:

■ UART0: 0x4000.C000

Note that the UART module clock must be enabled before the registers can be programmed (see page 210). There must be a delay of 3 system clocks after the UART module clock is enabled before any UART module registers are accessed.

Note: The UART must be disabled (see the UARTEN bit in the UARTCTL register on page 413) before any of the control registers are reprogrammed. When the UART is disabled during a TX or RX operation, the current transaction is completed prior to the UART stopping.

Table 11-3. UART Register Map

Offset	Name	Type	Reset	Description	See page
0x000	UARTDR	R/W	0x0000.0000	UART Data	402
0x004	UARTRSR/UARTECR	R/W	0x0000.0000	UART Receive Status/Error Clear	404
0x018	UARTFR	RO	0x0000.0090	UART Flag	406
0x020	UARTILPR	R/W	0x0000.0000	UART IrDA Low-Power Register	408
0x024	UARTIBRD	R/W	0x0000.0000	UART Integer Baud-Rate Divisor	409
0x028	UARTFBRD	R/W	0x0000.0000	UART Fractional Baud-Rate Divisor	410
0x02C	UARTLCRH	R/W	0x0000.0000	UART Line Control	411
0x030	UARTCTL	R/W	0x0000.0300	UART Control	413

Table 11-3. UART Register Map (continued)

Offset	Name	Туре	Reset	Description	See page
0x034	UARTIFLS	R/W	0x0000.0012	UART Interrupt FIFO Level Select	415
0x038	UARTIM	R/W	0x0000.0000	UART Interrupt Mask	417
0x03C	UARTRIS	RO	0x0000.000F	UART Raw Interrupt Status	419
0x040	UARTMIS	RO	0x0000.0000	UART Masked Interrupt Status	420
0x044	UARTICR	W1C	0x0000.0000	UART Interrupt Clear	421
0xFD0	UARTPeriphID4	RO	0x0000.0000	UART Peripheral Identification 4	423
0xFD4	UARTPeriphID5	RO	0x0000.0000	UART Peripheral Identification 5	424
0xFD8	UARTPeriphID6	RO	0x0000.0000	UART Peripheral Identification 6	425
0xFDC	UARTPeriphID7	RO	0x0000.0000	UART Peripheral Identification 7	426
0xFE0	UARTPeriphID0	RO	0x0000.0011	UART Peripheral Identification 0	427
0xFE4	UARTPeriphID1	RO	0x0000.0000	UART Peripheral Identification 1	428
0xFE8	UARTPeriphID2	RO	0x0000.0018	UART Peripheral Identification 2	429
0xFEC	UARTPeriphID3	RO	0x0000.0001	UART Peripheral Identification 3	430
0xFF0	UARTPCellID0	RO	0x0000.000D	UART PrimeCell Identification 0	431
0xFF4	UARTPCellID1	RO	0x0000.00F0	UART PrimeCell Identification 1	432
0xFF8	UARTPCellID2	RO	0x0000.0005	UART PrimeCell Identification 2	433
0xFFC	UARTPCellID3	RO	0x0000.00B1	UART PrimeCell Identification 3	434

## 11.6 Register Descriptions

The remainder of this section lists and describes the UART registers, in numerical order by address offset.

### Register 1: UART Data (UARTDR), offset 0x000

**Important:** This register is read-sensitive. See the register description for details.


This register is the data register (the interface to the FIFOs).

When FIFOs are enabled, data written to this location is pushed onto the transmit FIFO. If FIFOs are disabled, data is stored in the transmitter holding register (the bottom word of the transmit FIFO). A write to this register initiates a transmission from the UART.

For received data, if the FIFO is enabled, the data byte and the 4-bit status (break, frame, parity, and overrun) is pushed onto the 12-bit wide receive FIFO. If FIFOs are disabled, the data byte and status are stored in the receiving holding register (the bottom word of the receive FIFO). The received data can be retrieved by reading this register.

#### **UART Data (UARTDR)**

UART0 base: 0x4000.C000 Offset 0x000



Bit/Field	Name	Туре	Reset	Description
31:12	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
11	OE	RO	0	UART Overrun Error The OE values are defined as follows:
				Value Description
				0 There has been no data loss due to a FIFO overrun.
				New data was received when the FIFO was full, resulting in data loss.
10	BE	RO	0	UART Break Error This bit is set to 1 when a break condition is detected, indicating that

This bit is set to 1 when a break condition is detected, indicating that the receive data input was held Low for longer than a full-word transmission time (defined as start, data, parity, and stop bits).

In FIFO mode, this error is associated with the character at the top of the FIFO. When a break occurs, only one 0 character is loaded into the FIFO. The next character is only enabled after the received data input goes to a 1 (marking state) and the next valid start bit is received.

Bit/Field	Name	Туре	Reset	Description
9	PE	RO	0	UART Parity Error This bit is set to 1 when the parity of the received data character does not match the parity defined by bits 2 and 7 of the <b>UARTLCRH</b> register. In FIFO mode, this error is associated with the character at the top of the FIFO.
8	FE	RO	0	UART Framing Error This bit is set to 1 when the received character does not have a valid stop bit (a valid stop bit is 1).
7:0	DATA	R/W	0	Data Transmitted or Received  When written, the data that is to be transmitted via the UART. When read, the data that was received by the UART.

# Register 2: UART Receive Status/Error Clear (UARTRSR/UARTECR), offset 0x004

The **UARTRSR/UARTECR** register is the receive status register/error clear register.

In addition to the **UARTDR** register, receive status can also be read from the **UARTRSR** register. If the status is read from this register, then the status information corresponds to the entry read from **UARTDR** prior to reading **UARTRSR**. The status information for overrun is set immediately when an overrun condition occurs.

The **UARTRSR** register cannot be written.


A write of any value to the **UARTECR** register clears the framing, parity, break, and overrun errors. All the bits are cleared to 0 on reset.

#### Reads

UART Receive Status/Error Clear (UARTRSR/UARTECR)

UART0 base: 0x4000.C000 Offset 0x004

Type RO, reset 0x0000.0000



Bit/Field	Name	Туре	Reset	Description
31:4	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
3	OE	RO	0	UART Overrun Error When this bit is set to 1, data is received and the FIFO is already full. This bit is cleared to 0 by a write to <b>UARTECR</b> .
				The FIFO contents remain valid since no further data is written when the FIFO is full, only the contents of the shift register are overwritten. The CPU must now read the data in order to empty the FIFO.
2	BE	RO	0	UART Break Error

This bit is set to 1 when a break condition is detected, indicating that the received data input was held Low for longer than a full-word transmission time (defined as start, data, parity, and stop bits).

This bit is cleared to 0 by a write to **UARTECR**.

In FIFO mode, this error is associated with the character at the top of the FIFO. When a break occurs, only one 0 character is loaded into the FIFO. The next character is only enabled after the receive data input goes to a 1 (marking state) and the next valid start bit is received.

Bit/Field	Name	Туре	Reset	Description
1	PE	RO	0	UART Parity Error
				This bit is set to 1 when the parity of the received data character does not match the parity defined by bits 2 and 7 of the <b>UARTLCRH</b> register.
				This bit is cleared to 0 by a write to <b>UARTECR</b> .
0	FE	RO	0	UART Framing Error
				This bit is set to 1 when the received character does not have a valid stop bit (a valid stop bit is 1).

This bit is cleared to 0 by a write to **UARTECR**.

In FIFO mode, this error is associated with the character at the top of the FIFO.

#### Writes

#### UART Receive Status/Error Clear (UARTRSR/UARTECR)

UART0 base: 0x4000.C000 Offset 0x004 Type WO, reset 0x0000.0000

	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16
							1	rese	rved				1	'		•
Type	WO	WO	WO	WO	WO	WO	WO	WO	WO	WO	WO	WO	WO	WO	WO	WO
Reset	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0
	15	14	13	12	11	10	9	8	7	6	5	4	3	2	1	0
	reserved							DATA					'			
Туре	WO	WO	WO	WO	WO	WO	WO	WO	WO	WO	WO	WO	WO	WO	WO	WO
Reset	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0

Bit/Field	Name	Туре	Reset	Description
31:8	reserved	WO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
7:0	DATA	WO	0	Error Clear


A write to this register of any data clears the framing, parity, break, and overrun flags.

### Register 3: UART Flag (UARTFR), offset 0x018

The UARTFR register is the flag register. After reset, the TXFF, RXFF, and BUSY bits are 0, and TXFE and RXFE bits are 1.

#### **UART Flag (UARTFR)**

UART0 base: 0x4000.C000 Offset 0x018 Type RO, reset 0x0000.0090



Bit/Field	Name	Туре	Reset	Description
31:8	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
7	TXFE	RO	1	UART Transmit FIFO Empty
				The meaning of this bit depends on the state of the FEN bit in the <b>UARTLCRH</b> register.
				If the FIFO is disabled (FEN is 0), this bit is set when the transmit holding register is empty.
				If the FIFO is enabled (FEN is 1), this bit is set when the transmit FIFO is empty.
6	RXFF	RO	0	UART Receive FIFO Full
				The meaning of this bit depends on the state of the FEN bit in the <b>UARTLCRH</b> register.
				If the FIFO is disabled, this bit is set when the receive holding register is full.
				If the FIFO is enabled, this bit is set when the receive FIFO is full.
5	TXFF	RO	0	UART Transmit FIFO Full
				The meaning of this bit depends on the state of the FEN bit in the <b>UARTLCRH</b> register.
				If the FIFO is disabled, this bit is set when the transmit holding register is full.
				If the FIFO is enabled, this bit is set when the transmit FIFO is full.
4	RXFE	RO	1	UART Receive FIFO Empty
				The meaning of this bit depends on the state of the FEN bit in the <b>UARTLCRH</b> register.
				If the FIFO is disabled, this bit is set when the receive holding register is empty.
				If the FIFO is enabled, this bit is set when the receive FIFO is empty.

Bit/Field	Name	Type	Reset	Description
3	BUSY	RO	0	UART Busy When this bit is 1, the UART is busy transmitting data. This bit remains set until the complete byte, including all stop bits, has been sent from the shift register.
				This bit is set as soon as the transmit FIFO becomes non-empty (regardless of whether UART is enabled).
2:0	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.

### Register 4: UART IrDA Low-Power Register (UARTILPR), offset 0x020

The **UARTILPR** register is an 8-bit read/write register that stores the low-power counter divisor value used to derive the low-power SIR pulse width clock by dividing down the system clock (SysClk). All the bits are cleared to 0 when reset.

The internal IrlpBaud16 clock is generated by dividing down SysClk according to the low-power divisor value written to **UARTILPR**. The duration of SIR pulses generated when low-power mode is enabled is three times the period of the IrlpBaud16 clock. The low-power divisor value is calculated as follows:

ILPDVSR = SysClk / F<sub>IrLPBaud16</sub>

where F<sub>Trt.PBaud16</sub> is nominally 1.8432 MHz.


You must choose the divisor so that  $1.42\,\mathrm{MHz} < \mathrm{F}_{\mathtt{IrlPBaud16}} < 2.12\,\mathrm{MHz}$ , which results in a low-power pulse duration of  $1.41-2.11\,\mu s$  (three times the period of  $\mathtt{IrlPBaud16}$ ). The minimum frequency of  $\mathtt{IrlPBaud16}$  ensures that pulses less than one period of  $\mathtt{IrlPBaud16}$  are rejected, but that pulses greater than  $1.4\,\mu s$  are accepted as valid pulses.

**Note:** Zero is an illegal value. Programming a zero value results in no IrLPBaud16 pulses being generated.

#### UART IrDA Low-Power Register (UARTILPR)

UART0 base: 0x4000.C000 Offset 0x020

Type R/W, reset 0x0000.0000



Bit/Field	Name	Type	Reset	Description
31:8	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
7:0	ILPDVSR	R/W	0x00	IrDA Low-Power Divisor

This is an 8-bit low-power divisor value.

### Register 5: UART Integer Baud-Rate Divisor (UARTIBRD), offset 0x024

The **UARTIBRD** register is the integer part of the baud-rate divisor value. All the bits are cleared on reset. The minimum possible divide ratio is 1 (when **UARTIBRD**=0), in which case the **UARTFBRD** register is ignored. When changing the **UARTIBRD** register, the new value does not take effect until transmission/reception of the current character is complete. Any changes to the baud-rate divisor must be followed by a write to the **UARTLCRH** register. See "Baud-Rate Generation" on page 395 for configuration details.

#### UART Integer Baud-Rate Divisor (UARTIBRD)

UART0 base: 0x4000.C000 Offset 0x024

Type R/W, reset 0x0000.0000

.,,,,	7,96 1011,10001 5.100010000															
	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16
	reserved															
Туре	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO
Reset	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0
	15	14	13	12	11	10	9	8	7	6	5	4	3	2	1	0
	DIVINT													'		
Туре	R/W	R/W	R/W	R/W	R/W	R/W	R/W	R/W	R/W	R/W	R/W	R/W	R/W	R/W	R/W	R/W
Reset	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0
E	Bit/Field Name Type Reset		Des	cription												
	31:16 reserved RO 0				Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.											
	15:0		DIVII	NT	R/	W	0x0000	Integer Baud-Rate Divisor								

### Register 6: UART Fractional Baud-Rate Divisor (UARTFBRD), offset 0x028

The **UARTFBRD** register is the fractional part of the baud-rate divisor value. All the bits are cleared on reset. When changing the **UARTFBRD** register, the new value does not take effect until transmission/reception of the current character is complete. Any changes to the baud-rate divisor must be followed by a write to the **UARTLCRH** register. See "Baud-Rate Generation" on page 395 for configuration details.

#### UART Fractional Baud-Rate Divisor (UARTFBRD)

**DIVFRAC** 


R/W

0x000

UART0 base: 0x4000.C000 Offset 0x028

Type R/W, reset 0x0000.0000

5:0



Fractional Baud-Rate Divisor


### Register 7: UART Line Control (UARTLCRH), offset 0x02C

The **UARTLCRH** register is the line control register. Serial parameters such as data length, parity, and stop bit selection are implemented in this register.

When updating the baud-rate divisor (UARTIBRD and/or UARTIFRD), the UARTLCRH register must also be written. The write strobe for the baud-rate divisor registers is tied to the UARTLCRH register.

#### UART Line Control (UARTLCRH)

UART0 base: 0x4000.C000 Offset 0x02C Type R/W, reset 0x0000.0000



Bit/Field	Name	Type	Reset	Description
31:8	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
7	SPS	R/W	0	UART Stick Parity Select When bits 1, 2, and 7 of <b>UARTLCRH</b> are set, the parity bit is transmitted and checked as a 0. When bits 1 and 7 are set and 2 is cleared, the parity bit is transmitted and checked as a 1. When this bit is cleared, stick parity is disabled.
6:5	WLEN	R/W	0	UART Word Length The bits indicate the number of data bits transmitted or received in a frame as follows:  Value Description 0x3 8 bits 0x2 7 bits 0x1 6 bits 0x0 5 bits (default)
4	FEN	R/W	0	UART Enable FIFOs  If this bit is set to 1, transmit and receive FIFO buffers are enabled (FIFO mode).  When cleared to 0, FIFOs are disabled (Character mode). The FIFOs become 1-byte-deep holding registers.
3	STP2	R/W	0	UART Two Stop Bits Select If this bit is set to 1, two stop bits are transmitted at the end of a frame. The receive logic does not check for two stop bits being received.

Bit/Field	Name	Туре	Reset	Description
2	EPS	R/W	0	UART Even Parity Select
				If this bit is set to 1, even parity generation and checking is performed during transmission and reception, which checks for an even number of 1s in data and parity bits.
				When cleared to 0, then odd parity is performed, which checks for an odd number of 1s.
				This bit has no effect when parity is disabled by the ${\tt PEN}$ bit.
1	PEN	R/W	0	UART Parity Enable
				If this bit is set to 1, parity checking and generation is enabled; otherwise, parity is disabled and no parity bit is added to the data frame.
0	BRK	R/W	0	UART Send Break
				If this bit is set to 1, a Low level is continually output on the ${\tt UnTX}$ output, after completing transmission of the current character. For the proper execution of the break command, the software must set this bit for at least two frames (character periods). For normal use, this bit must be cleared to 0.

#### Register 8: UART Control (UARTCTL), offset 0x030

The **UARTCTL** register is the control register. All the bits are cleared on reset except for the Transmit Enable (TXE) and Receive Enable (RXE) bits, which are set to 1.

To enable the UART module, the UARTEN bit must be set to 1. If software requires a configuration change in the module, the UARTEN bit must be cleared before the configuration changes are written. If the UART is disabled during a transmit or receive operation, the current transaction is completed prior to the UART stopping.

**Note:** The **UARTCTL** register should not be changed while the UART is enabled or else the results are unpredictable. The following sequence is recommended for making changes to the **UARTCTL** register.


- 1. Disable the UART.
- 2. Wait for the end of transmission or reception of the current character.
- 3. Flush the transmit FIFO by disabling bit 4 (FEN) in the line control register (UARTLCRH).
- **4.** Reprogram the control register.
- 5. Enable the UART.

#### **UART Control (UARTCTL)**

UART0 base: 0x4000.C000

Offset 0x030

Type R/W, reset 0x0000.0300



Bit/Field	Name	Type	Reset	Description
Ditt icia	Hame	1900	110001	Description
31:10	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
9	RXE	R/W	1	UART Receive Enable
				If this bit is set to 1, the receive section of the UART is enabled. When the UART is disabled in the middle of a receive, it completes the current character before stopping.
				Note: To enable reception, the UARTEN bit must also be set.
8	TXE	R/W	1	UART Transmit Enable
				If this bit is set to 1, the transmit section of the UART is enabled. When the UART is disabled in the middle of a transmission, it completes the current character before stopping.

**Note:** To enable transmission, the UARTEN bit must also be set.

Bit/Field	Name	Туре	Reset	Description
7	LBE	R/W	0	UART Loop Back Enable If this bit is set to 1, the ${\tt UnTX}$ path is fed through the ${\tt UnRX}$ path.
6:3	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
2	SIRLP	R/W	0	UART SIR Low Power Mode
				This bit selects the IrDA encoding mode. If this bit is cleared to 0, low-level bits are transmitted as an active High pulse with a width of 3/16th of the bit period. If this bit is set to 1, low-level bits are transmitted with a pulse width which is 3 times the period of the IrLPBaud16 input signal, regardless of the selected bit rate. Setting this bit uses less power, but might reduce transmission distances. See page 408 for more information.
1	SIREN	R/W	0	UART SIR Enable
				If this bit is set to 1, the IrDA SIR block is enabled, and the UART will transmit and receive data using SIR protocol.
0	UARTEN	R/W	0	UART Enable  If this bit is set to 1, the UART is enabled. When the UART is disabled in the middle of transmission or reception, it completes the current character before stopping.

### Register 9: UART Interrupt FIFO Level Select (UARTIFLS), offset 0x034


The **UARTIFLS** register is the interrupt FIFO level select register. You can use this register to define the FIFO level at which the TXRIS and RXRIS bits in the **UARTRIS** register are triggered.

The interrupts are generated based on a transition through a level rather than being based on the level. That is, the interrupts are generated when the fill level progresses through the trigger level. For example, if the receive trigger level is set to the half-way mark, the interrupt is triggered as the module is receiving the 9th character.

Out of reset, the TXIFLSEL and RXIFLSEL bits are configured so that the FIFOs trigger an interrupt at the half-way mark.

#### UART Interrupt FIFO Level Select (UARTIFLS)

UART0 base: 0x4000.C000 Offset 0x034 Type R/W, reset 0x0000.0012



Bit/Field	Name	Type	Reset	Description
31:6	reserved	RO	0x00	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
5:3	RXIFLSEL	R/W	0x2	UART Receive Interrupt FIFO Level Select

The trigger points for the receive interrupt are as follows:

Value	Description
0x0	RX FIFO ≥ 1/8 full
0x1	RX FIFO ≥ ¼ full
0x2	RX FIFO ≥ ½ full (default)
0x3	RX FIFO ≥ ¾ full
0x4	RX FIFO ≥ 7/8 full
0x5-0x7	Reserved

Bit/Field	Name	Type	Reset	Description	on
2:0	TXIFLSEL	R/W	0x2	UART Tra	ansmit Interrupt FIFO Level Select er points for the transmit interrupt are as follows:  Description  TX FIFO ≤ ¼ empty  TX FIFO ≤ ½ empty  TX FIFO ≤ ½ empty (default)  TX FIFO ≤ ¼ empty
				0x4 0x5-0x7	TX FIFO ≤ 1/2 empty  Reserved

### Register 10: UART Interrupt Mask (UARTIM), offset 0x038

The **UARTIM** register is the interrupt mask set/clear register.

On a read, this register gives the current value of the mask on the relevant interrupt. Writing a 1 to a bit allows the corresponding raw interrupt signal to be routed to the interrupt controller. Writing a 0 prevents the raw interrupt signal from being sent to the interrupt controller.

#### UART Interrupt Mask (UARTIM)

UART0 base: 0x4000.C000

Offset 0x038

Type R/W, reset 0x0000.0000

	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16
								rese	rved							•
Type	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO
Reset	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0
	15	14	13	12	11	10	9	8	7	6	5	4	3	2	1	0
			reserved		ı	OEIM	BEIM	PEIM	FEIM	RTIM	TXIM	RXIM		rese	rved	1
Type	RO	RO	RO	RO	RO	R/W	RO	RO	RO	RO						
Reset	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0

Bit/Field	Name	Туре	Reset	Description
31:11	reserved	RO	0x00	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
10	OEIM	R/W	0	UART Overrun Error Interrupt Mask On a read, the current mask for the OEIM interrupt is returned. Setting this bit to 1 promotes the OEIM interrupt to the interrupt controller.
9	BEIM	R/W	0	UART Break Error Interrupt Mask On a read, the current mask for the BEIM interrupt is returned. Setting this bit to 1 promotes the BEIM interrupt to the interrupt controller.
8	PEIM	R/W	0	UART Parity Error Interrupt Mask On a read, the current mask for the PEIM interrupt is returned. Setting this bit to 1 promotes the PEIM interrupt to the interrupt controller.
7	FEIM	R/W	0	UART Framing Error Interrupt Mask On a read, the current mask for the FEIM interrupt is returned. Setting this bit to 1 promotes the FEIM interrupt to the interrupt controller.
6	RTIM	R/W	0	UART Receive Time-Out Interrupt Mask On a read, the current mask for the RTIM interrupt is returned. Setting this bit to 1 promotes the RTIM interrupt to the interrupt controller.
5	TXIM	R/W	0	UART Transmit Interrupt Mask On a read, the current mask for the TXIM interrupt is returned. Setting this bit to 1 promotes the TXIM interrupt to the interrupt controller.
4	RXIM	R/W	0	UART Receive Interrupt Mask On a read, the current mask for the RXIM interrupt is returned. Setting this bit to 1 promotes the RXIM interrupt to the interrupt controller.

Bit/Field	Name	Type	Reset	Description
3:0	reserved	RO	0x00	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.

RO 1

RO

RO

### Register 11: UART Raw Interrupt Status (UARTRIS), offset 0x03C

The **UARTRIS** register is the raw interrupt status register. On a read, this register gives the current raw status value of the corresponding interrupt. A write has no effect.

#### **UART Raw Interrupt Status (UARTRIS)**

UART0 base: 0x4000.C000 Offset 0x03C Type RO, reset 0x0000.000F

> RO 0

Туре

0

Reset

RO 0 RO 0

	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16
		,						rese	rved							'
Туре	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO
Reset	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0
	15	14	13	12	11	10	9	8	7	6	5	4	3	2	1	0
		1	reserved			OERIS	BERIS	PERIS	FERIS	RTRIS	TXRIS	RXRIS		rese	rved	

Bit/Field	Name	Type	Reset	Description
31:11	reserved	RO	0x00	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
10	OERIS	RO	0	UART Overrun Error Raw Interrupt Status
				Gives the raw interrupt state (prior to masking) of this interrupt.
9	BERIS	RO	0	UART Break Error Raw Interrupt Status
				Gives the raw interrupt state (prior to masking) of this interrupt.
8	PERIS	RO	0	UART Parity Error Raw Interrupt Status
				Gives the raw interrupt state (prior to masking) of this interrupt.
7	FERIS	RO	0	UART Framing Error Raw Interrupt Status
				Gives the raw interrupt state (prior to masking) of this interrupt.
6	RTRIS	RO	0	UART Receive Time-Out Raw Interrupt Status
				Gives the raw interrupt state (prior to masking) of this interrupt.
5	TXRIS	RO	0	UART Transmit Raw Interrupt Status
				Gives the raw interrupt state (prior to masking) of this interrupt.
4	RXRIS	RO	0	UART Receive Raw Interrupt Status
				Gives the raw interrupt state (prior to masking) of this interrupt.
3:0	reserved	RO	0xF	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.

### Register 12: UART Masked Interrupt Status (UARTMIS), offset 0x040

The **UARTMIS** register is the masked interrupt status register. On a read, this register gives the current masked status value of the corresponding interrupt. A write has no effect.

UART Masked Interrupt Status (UARTMIS)

UART0 base: 0x4000.C000 Offset 0x040 Type RO, reset 0x0000.0000

_	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16
ſ			1		1			rese	rved							
Type	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO
Reset	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0
	15	14	13	12	11	10	9	8	7	6	5	4	3	2	1	0
		•	reserved	'	' !	OEMIS	BEMIS	PEMIS	FEMIS	RTMIS	TXMIS	RXMIS		rese	rved	•
Туре	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO
Reset	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0

Bit/Field	Name	Туре	Reset	Description
31:11	reserved	RO	0x00	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
10	OEMIS	RO	0	UART Overrun Error Masked Interrupt Status Gives the masked interrupt state of this interrupt.
9	BEMIS	RO	0	UART Break Error Masked Interrupt Status Gives the masked interrupt state of this interrupt.
8	PEMIS	RO	0	UART Parity Error Masked Interrupt Status Gives the masked interrupt state of this interrupt.
7	FEMIS	RO	0	UART Framing Error Masked Interrupt Status Gives the masked interrupt state of this interrupt.
6	RTMIS	RO	0	UART Receive Time-Out Masked Interrupt Status Gives the masked interrupt state of this interrupt.
5	TXMIS	RO	0	UART Transmit Masked Interrupt Status Gives the masked interrupt state of this interrupt.
4	RXMIS	RO	0	UART Receive Masked Interrupt Status Gives the masked interrupt state of this interrupt.
3:0	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.

### Register 13: UART Interrupt Clear (UARTICR), offset 0x044

The **UARTICR** register is the interrupt clear register. On a write of 1, the corresponding interrupt (both raw interrupt and masked interrupt, if enabled) is cleared. A write of 0 has no effect.

#### **UART Interrupt Clear (UARTICR)**

UART0 base: 0x4000.C000 Offset 0x044 Type W1C, reset 0x0000.0000

	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16
		l	ı					rese	rved							
Type Reset	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0
	15	14	13	12	11	10	9	8	7	6	5	4	3	2	1	0
		'	reserved			OEIC	BEIC	PEIC	FEIC	RTIC	TXIC	RXIC		rese	rved	
Type Reset	RO 0	RO 0	RO 0	RO 0	RO 0	W1C 0	RO 0	RO 0	RO 0	RO 0						

et U U	) 0 0	0 0	U	
Bit/Field	Name	Туре	Reset	Description
31:11	reserved	RO	0x00	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
10	OEIC	W1C	0	Overrun Error Interrupt Clear
				The OEIC values are defined as follows:
				Value Description
				0 No effect on the interrupt.
				1 Clears interrupt.
9	BEIC	W1C	0	Break Error Interrupt Clear
				The BEIC values are defined as follows:
				Value Description
				0 No effect on the interrupt.
				1 Clears interrupt.
8	PEIC	W1C	0	Parity Error Interrupt Clear
				The PEIC values are defined as follows:
				Value Description
				0 No effect on the interrupt.
				1 Clears interrupt.
7	FEIC	W1C	0	Framing Error Interrupt Clear
				The FEIC values are defined as follows:
				Value Description
				O No offect on the interrupt

- No effect on the interrupt.
- Clears interrupt.


Bit/Field	Name	Туре	Reset	Description
6	RTIC	W1C	0	Receive Time-Out Interrupt Clear The RTIC values are defined as follows:
				Value Description  0 No effect on the interrupt.  1 Clears interrupt.
5	TXIC	W1C	0	Transmit Interrupt Clear The TXIC values are defined as follows:  Value Description  0 No effect on the interrupt.  1 Clears interrupt.
4	RXIC	W1C	0	Receive Interrupt Clear The RXIC values are defined as follows:  Value Description  0 No effect on the interrupt.  1 Clears interrupt.
3:0	reserved	RO	0x00	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.

### Register 14: UART Peripheral Identification 4 (UARTPeriphID4), offset 0xFD0

The **UARTPeriphIDn** registers are hard-coded and the fields within the registers determine the reset values.

#### UART Peripheral Identification 4 (UARTPeriphID4)

UART0 base: 0x4000.C000 Offset 0xFD0 Type RO, reset 0x0000.0000




Bit/Field	Name	Type	Reset	Description
31:8	reserved	RO	0x00	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
7:0	PID4	RO	0x0000	UART Peripheral ID Register[7:0]

### Register 15: UART Peripheral Identification 5 (UARTPeriphID5), offset 0xFD4

The **UARTPeriphIDn** registers are hard-coded and the fields within the registers determine the reset values.

UART Peripheral Identification 5 (UARTPeriphID5)

UART0 base: 0x4000.C000 Offset 0xFD4 Type RO, reset 0x0000.0000




Bit/Field	Name	Type	Reset	Description
31:8	reserved	RO	0x00	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
7:0	PID5	RO	0x0000	UART Peripheral ID Register[15:8]

### Register 16: UART Peripheral Identification 6 (UARTPeriphID6), offset 0xFD8

The **UARTPeriphIDn** registers are hard-coded and the fields within the registers determine the reset values.

UART Peripheral Identification 6 (UARTPeriphID6)

UART0 base: 0x4000.C000 Offset 0xFD8 Type RO, reset 0x0000.0000




Bit/Field	Name	Type	Reset	Description
31:8	reserved	RO	0x00	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
7:0	PID6	RO	0x0000	UART Peripheral ID Register[23:16]

### Register 17: UART Peripheral Identification 7 (UARTPeriphID7), offset 0xFDC

The **UARTPeriphIDn** registers are hard-coded and the fields within the registers determine the reset values.

UART Peripheral Identification 7 (UARTPeriphID7)

UART0 base: 0x4000.C000 Offset 0xFDC Type RO, reset 0x0000.0000




Bit/Field	Name	Type	Reset	Description
31:8	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
7:0	PID7	RO	0x0000	UART Peripheral ID Register[31:24]

### Register 18: UART Peripheral Identification 0 (UARTPeriphID0), offset 0xFE0

The **UARTPeriphIDn** registers are hard-coded and the fields within the registers determine the reset values.

#### UART Peripheral Identification 0 (UARTPeriphID0)

UART0 base: 0x4000.C000 Offset 0xFE0 Type RO, reset 0x0000.0011




Bit/Field	Name	Type	Reset	Description
31:8	reserved	RO	0x00	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
7:0	PID0	RO	0x11	UART Peripheral ID Register[7:0]

### Register 19: UART Peripheral Identification 1 (UARTPeriphID1), offset 0xFE4

The **UARTPeriphIDn** registers are hard-coded and the fields within the registers determine the reset values.

UART Peripheral Identification 1 (UARTPeriphID1)

UART0 base: 0x4000.C000 Offset 0xFE4 Type RO, reset 0x0000.0000




Bit/Field	Name	Type	Reset	Description
31:8	reserved	RO	0x00	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
7:0	PID1	RO	0x00	UART Peripheral ID Register[15:8]

### Register 20: UART Peripheral Identification 2 (UARTPeriphID2), offset 0xFE8

The **UARTPeriphIDn** registers are hard-coded and the fields within the registers determine the reset values.

UART Peripheral Identification 2 (UARTPeriphID2)

UART0 base: 0x4000.C000 Offset 0xFE8 Type RO, reset 0x0000.0018




Bit/Field	Name	Type	Reset	Description
31:8	reserved	RO	0x00	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
7:0	PID2	RO	0x18	UART Peripheral ID Register[23:16]

### Register 21: UART Peripheral Identification 3 (UARTPeriphID3), offset 0xFEC

The **UARTPeriphIDn** registers are hard-coded and the fields within the registers determine the reset values.

UART Peripheral Identification 3 (UARTPeriphID3)

UART0 base: 0x4000.C000 Offset 0xFEC Type RO, reset 0x0000.0001




Bit/Field	Name	Type	Reset	Description
31:8	reserved	RO	0x00	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
7:0	PID3	RO	0x01	UART Peripheral ID Register[31:24]

### Register 22: UART PrimeCell Identification 0 (UARTPCellID0), offset 0xFF0

The **UARTPCellIDn** registers are hard-coded and the fields within the registers determine the reset values.

#### UART PrimeCell Identification 0 (UARTPCellID0)

UART0 base: 0x4000.C000 Offset 0xFF0 Type RO, reset 0x0000.000D



Bit/Field	Name	Type	Reset	Description
31:8	reserved	RO	0x00	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
7:0	CID0	RO	0x0D	UART PrimeCell ID Register[7:0]


Provides software a standard cross-peripheral identification system.

### Register 23: UART PrimeCell Identification 1 (UARTPCellID1), offset 0xFF4

The **UARTPCellIDn** registers are hard-coded and the fields within the registers determine the reset values.

#### UART PrimeCell Identification 1 (UARTPCellID1)

UART0 base: 0x4000.C000 Offset 0xFF4 Type RO, reset 0x0000.00F0



Bit/Field	Name	Type	Reset	Description
31:8	reserved	RO	0x00	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
7:0	CID1	RO	0xF0	UART PrimeCell ID Register[15:8]


Provides software a standard cross-peripheral identification system.

# Register 24: UART PrimeCell Identification 2 (UARTPCellID2), offset 0xFF8

The **UARTPCellIDn** registers are hard-coded and the fields within the registers determine the reset values.

#### UART PrimeCell Identification 2 (UARTPCellID2)

UART0 base: 0x4000.C000 Offset 0xFF8 Type RO, reset 0x0000.0005



Bit/Field	Name	Type	Reset	Description
31:8	reserved	RO	0x00	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
7:0	CID2	RO	0x05	UART PrimeCell ID Register[23:16]


Provides software a standard cross-peripheral identification system.

# Register 25: UART PrimeCell Identification 3 (UARTPCellID3), offset 0xFFC

The **UARTPCellIDn** registers are hard-coded and the fields within the registers determine the reset values.

### UART PrimeCell Identification 3 (UARTPCellID3)

UART0 base: 0x4000.C000 Offset 0xFFC Type RO, reset 0x0000.00B1



Bit/Field	Name	Type	Reset	Description
31:8	reserved	RO	0x00	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
7:0	CID3	RO	0xB1	UART PrimeCell ID Register[31:24]

Provides software a standard cross-peripheral identification system.

# 12 Synchronous Serial Interface (SSI)


The Stellaris® Synchronous Serial Interface (SSI) is a master or slave interface for synchronous serial communication with peripheral devices that have either Freescale SPI, MICROWIRE, or Texas Instruments synchronous serial interfaces.

The Stellaris SSI module has the following features:

- Master or slave operation
- Programmable clock bit rate and prescale
- Separate transmit and receive FIFOs, 16 bits wide, 8 locations deep
- Programmable interface operation for Freescale SPI, MICROWIRE, or Texas Instruments synchronous serial interfaces
- Programmable data frame size from 4 to 16 bits
- Internal loopback test mode for diagnostic/debug testing

# 12.1 Block Diagram

Figure 12-1. SSI Module Block Diagram



# 12.2 Signal Description

Table 12-1 on page 436 and Table 12-2 on page 436 list the external signals of the SSI module and describe the function of each. The SSI signals are alternate functions for some GPIO signals and

default to be GPIO signals at reset., with the exception of the SSIOClk, SSIOFSS, SSIORX, and SSIOTX pins which default to the SSI function. The column in the table below titled "Pin Assignment" lists the possible GPIO pin placements for the SSI signals. The AFSEL bit in the **GPIO Alternate** Function Select (GPIOAFSEL) register (page 272) should be set to choose the SSI function. For more information on configuring GPIOs, see "General-Purpose Input/Outputs (GPIOS)" on page 251.

Table 12-1. SSI Signals (100LQFP)

Pin Name	Pin Number	Pin Type	Buffer Type <sup>a</sup>	Description
SSIOClk	28	I/O	TTL	SSI module 0 clock.
SSIOFss	29	I/O	TTL	SSI module 0 frame.
SSI0Rx	30	I	TTL	SSI module 0 receive.
SSIOTx	31	0	TTL	SSI module 0 transmit.

a. The TTL designation indicates the pin has TTL-compatible voltage levels.

Table 12-2. SSI Signals (108BGA)

Pin Name	Pin Number	Pin Type	Buffer Type <sup>a</sup>	Description
SSIOClk	M4	I/O	TTL	SSI module 0 clock.
SSI0Fss	L4	I/O	TTL	SSI module 0 frame.
SSIORx	L5	1	TTL	SSI module 0 receive.
SSIOTx	M5	0	TTL	SSI module 0 transmit.

a. The TTL designation indicates the pin has TTL-compatible voltage levels.

# 12.3 Functional Description

The SSI performs serial-to-parallel conversion on data received from a peripheral device. The CPU accesses data, control, and status information. The transmit and receive paths are buffered with internal FIFO memories allowing up to eight 16-bit values to be stored independently in both transmit and receive modes.

#### 12.3.1 Bit Rate Generation

The SSI includes a programmable bit rate clock divider and prescaler to generate the serial output clock. Bit rates are supported to 2 MHz and higher, although maximum bit rate is determined by peripheral devices.

The serial bit rate is derived by dividing down the input clock (FSysClk). The clock is first divided by an even prescale value CPSDVSR from 2 to 254, which is programmed in the **SSI Clock Prescale** (**SSICPSR**) register (see page 455). The clock is further divided by a value from 1 to 256, which is 1 + SCR, where SCR is the value programmed in the **SSI Control0** (**SSICR0**) register (see page 448).

The frequency of the output clock SSIClk is defined by:

```
SSIClk = FSysClk / (CPSDVSR * (1 + SCR))
```

**Note:** For master mode, the system clock must be at least two times faster than the SSIClk. For slave mode, the system clock must be at least 12 times faster than the SSIClk.

See "Synchronous Serial Interface (SSI)" on page 570 to view SSI timing parameters.

### 12.3.2 FIFO Operation

#### 12.3.2.1 Transmit FIFO

The common transmit FIFO is a 16-bit wide, 8-locations deep, first-in, first-out memory buffer. The CPU writes data to the FIFO by writing the **SSI Data (SSIDR)** register (see page 452), and data is stored in the FIFO until it is read out by the transmission logic.

When configured as a master or a slave, parallel data is written into the transmit FIFO prior to serial conversion and transmission to the attached slave or master, respectively, through the SSITX pin.

In slave mode, the SSI transmits data each time the master initiates a transaction. If the transmit FIFO is empty and the master initiates, the slave transmits the 8th most recent value in the transmit FIFO. If less than 8 values have been written to the transmit FIFO since the SSI module clock was enabled using the SSI bit in the **RGCG1** register, then 0 is transmitted. Care should be taken to ensure that valid data is in the FIFO as needed. The SSI can be configured to generate an interrupt or a  $\mu$ DMA request when the FIFO is empty.

#### 12.3.2.2 Receive FIFO

The common receive FIFO is a 16-bit wide, 8-locations deep, first-in, first-out memory buffer. Received data from the serial interface is stored in the buffer until read out by the CPU, which accesses the read FIFO by reading the **SSIDR** register.

When configured as a master or slave, serial data received through the SSIRx pin is registered prior to parallel loading into the attached slave or master receive FIFO, respectively.

### 12.3.3 Interrupts

The SSI can generate interrupts when the following conditions are observed:

- Transmit FIFO service
- Receive FIFO service
- Receive FIFO time-out
- Receive FIFO overrun

All of the interrupt events are ORed together before being sent to the interrupt controller, so the SSI can only generate a single interrupt request to the controller at any given time. You can mask each of the four individual maskable interrupts by setting the appropriate bits in the **SSI Interrupt Mask** (**SSIIM**) register (see page 456). Setting the appropriate mask bit to 1 enables the interrupt.

Provision of the individual outputs, as well as a combined interrupt output, allows use of either a global interrupt service routine, or modular device drivers to handle interrupts. The transmit and receive dynamic dataflow interrupts have been separated from the status interrupts so that data can be read or written in response to the FIFO trigger levels. The status of the individual interrupt sources can be read from the SSI Raw Interrupt Status (SSIRIS) and SSI Masked Interrupt Status (SSIMIS) registers (see page 458 and page 459, respectively).

#### 12.3.4 Frame Formats

Each data frame is between 4 and 16 bits long, depending on the size of data programmed, and is transmitted starting with the MSB. There are three basic frame types that can be selected:

Texas Instruments synchronous serial

- Freescale SPI
- MICROWIRE

For all three formats, the serial clock (SSIClk) is held inactive while the SSI is idle, and SSIClk transitions at the programmed frequency only during active transmission or reception of data. The idle state of SSIClk is utilized to provide a receive timeout indication that occurs when the receive FIFO still contains data after a timeout period.

For Freescale SPI and MICROWIRE frame formats, the serial frame (SSIFss) pin is active Low, and is asserted (pulled down) during the entire transmission of the frame.

For Texas Instruments synchronous serial frame format, the SSIFss pin is pulsed for one serial clock period starting at its rising edge, prior to the transmission of each frame. For this frame format, both the SSI and the off-chip slave device drive their output data on the rising edge of SSIClk, and latch data from the other device on the falling edge.

Unlike the full-duplex transmission of the other two frame formats, the MICROWIRE format uses a special master-slave messaging technique, which operates at half-duplex. In this mode, when a frame begins, an 8-bit control message is transmitted to the off-chip slave. During this transmit, no incoming data is received by the SSI. After the message has been sent, the off-chip slave decodes it and, after waiting one serial clock after the last bit of the 8-bit control message has been sent, responds with the requested data. The returned data can be 4 to 16 bits in length, making the total frame length anywhere from 13 to 25 bits.

### 12.3.4.1 Texas Instruments Synchronous Serial Frame Format

Figure 12-2 on page 438 shows the Texas Instruments synchronous serial frame format for a single transmitted frame.




Figure 12-2. TI Synchronous Serial Frame Format (Single Transfer)

In this mode, SSIClk and SSIFSS are forced Low, and the transmit data line SSITx is tristated whenever the SSI is idle. Once the bottom entry of the transmit FIFO contains data, SSIFSS is pulsed High for one SSIClk period. The value to be transmitted is also transferred from the transmit FIFO to the serial shift register of the transmit logic. On the next rising edge of SSIClk, the MSB of the 4 to 16-bit data frame is shifted out on the SSITx pin. Likewise, the MSB of the received data is shifted onto the SSIRx pin by the off-chip serial slave device.

Both the SSI and the off-chip serial slave device then clock each data bit into their serial shifter on the falling edge of each SSIClk. The received data is transferred from the serial shifter to the receive FIFO on the first rising edge of SSIClk after the LSB has been latched.

Figure 12-3 on page 439 shows the Texas Instruments synchronous serial frame format when back-to-back frames are transmitted.




Figure 12-3. TI Synchronous Serial Frame Format (Continuous Transfer)

#### 12.3.4.2 Freescale SPI Frame Format

The Freescale SPI interface is a four-wire interface where the SSIFss signal behaves as a slave select. The main feature of the Freescale SPI format is that the inactive state and phase of the SSIClk signal are programmable through the SPO and SPH bits within the **SSISCR0** control register.

#### SPO Clock Polarity Bit

When the SPO clock polarity control bit is Low, it produces a steady state Low value on the SSIClk pin. If the SPO bit is High, a steady state High value is placed on the SSIClk pin when data is not being transferred.

#### SPH Phase Control Bit

The SPH phase control bit selects the clock edge that captures data and allows it to change state. It has the most impact on the first bit transmitted by either allowing or not allowing a clock transition before the first data capture edge. When the SPH phase control bit is Low, data is captured on the first clock edge transition. If the SPH bit is High, data is captured on the second clock edge transition.

### 12.3.4.3 Freescale SPI Frame Format with SPO=0 and SPH=0

Single and continuous transmission signal sequences for Freescale SPI format with SPO=0 and SPH=0 are shown in Figure 12-4 on page 439 and Figure 12-5 on page 440.




Figure 12-4. Freescale SPI Format (Single Transfer) with SPO=0 and SPH=0

November 18, 2011 439




Figure 12-5. Freescale SPI Format (Continuous Transfer) with SPO=0 and SPH=0

In this configuration, during idle periods:

- SSIClk is forced Low
- SSIFss is forced High
- The transmit data line SSITx is arbitrarily forced Low
- When the SSI is configured as a master, it enables the SSIClk pad
- When the SSI is configured as a slave, it disables the SSIClk pad

If the SSI is enabled and there is valid data within the transmit FIFO, the start of transmission is signified by the SSIFss master signal being driven Low. This causes slave data to be enabled onto the SSIRx input line of the master. The master SSITx output pad is enabled.

One half SSIC1k period later, valid master data is transferred to the SSITx pin. Now that both the master and slave data have been set, the SSIC1k master clock pin goes High after one further half SSIC1k period.

The data is now captured on the rising and propagated on the falling edges of the SSIClk signal.

In the case of a single word transmission, after all bits of the data word have been transferred, the SSIFss line is returned to its idle High state one SSIC1k period after the last bit has been captured.

However, in the case of continuous back-to-back transmissions, the SSIFss signal must be pulsed High between each data word transfer. This is because the slave select pin freezes the data in its serial peripheral register and does not allow it to be altered if the SPH bit is logic zero. Therefore, the master device must raise the SSIFss pin of the slave device between each data transfer to enable the serial peripheral data write. On completion of the continuous transfer, the SSIFss pin is returned to its idle state one SSIClk period after the last bit has been captured.

### 12.3.4.4 Freescale SPI Frame Format with SPO=0 and SPH=1

The transfer signal sequence for Freescale SPI format with SPO=0 and SPH=1 is shown in Figure 12-6 on page 441, which covers both single and continuous transfers.

Figure 12-6. Freescale SPI Frame Format with SPO=0 and SPH=1

Note: Q is undefined.

In this configuration, during idle periods:

- SSIClk is forced Low
- SSIFss is forced High
- The transmit data line SSITx is arbitrarily forced Low
- When the SSI is configured as a master, it enables the SSIClk pad
- When the SSI is configured as a slave, it disables the SSIClk pad

If the SSI is enabled and there is valid data within the transmit FIFO, the start of transmission is signified by the SSIFss master signal being driven Low. The master SSITx output is enabled. After a further one half SSIC1k period, both master and slave valid data is enabled onto their respective transmission lines. At the same time, the SSIC1k is enabled with a rising edge transition.

Data is then captured on the falling edges and propagated on the rising edges of the SSIC1k signal.

In the case of a single word transfer, after all bits have been transferred, the SSIFss line is returned to its idle High state one SSIClk period after the last bit has been captured.

For continuous back-to-back transfers, the SSIFss pin is held Low between successive data words and termination is the same as that of the single word transfer.

#### 12.3.4.5 Freescale SPI Frame Format with SPO=1 and SPH=0

Single and continuous transmission signal sequences for Freescale SPI format with SPO=1 and SPH=0 are shown in Figure 12-7 on page 441 and Figure 12-8 on page 442.




Figure 12-7. Freescale SPI Frame Format (Single Transfer) with SPO=1 and SPH=0

Note: Q is undefined.

SSICIK

SSIFss

SSITx/SSIRx

LSB

MSB

4 to 16 bits

Figure 12-8. Freescale SPI Frame Format (Continuous Transfer) with SPO=1 and SPH=0

In this configuration, during idle periods:

- SSIClk is forced High
- SSIFss is forced High
- The transmit data line SSITx is arbitrarily forced Low
- When the SSI is configured as a master, it enables the SSIClk pad
- When the SSI is configured as a slave, it disables the SSIClk pad

If the SSI is enabled and there is valid data within the transmit FIFO, the start of transmission is signified by the SSIFss master signal being driven Low, which causes slave data to be immediately transferred onto the SSIRx line of the master. The master SSITx output pad is enabled.

One half period later, valid master data is transferred to the SSITx line. Now that both the master and slave data have been set, the SSIClk master clock pin becomes Low after one further half SSIClk period. This means that data is captured on the falling edges and propagated on the rising edges of the SSIClk signal.

In the case of a single word transmission, after all bits of the data word are transferred, the SSIFss line is returned to its idle High state one SSIClk period after the last bit has been captured.

However, in the case of continuous back-to-back transmissions, the SSIFss signal must be pulsed High between each data word transfer. This is because the slave select pin freezes the data in its serial peripheral register and does not allow it to be altered if the SPH bit is logic zero. Therefore, the master device must raise the SSIFss pin of the slave device between each data transfer to enable the serial peripheral data write. On completion of the continuous transfer, the SSIFss pin is returned to its idle state one SSIClk period after the last bit has been captured.

#### 12.3.4.6 Freescale SPI Frame Format with SPO=1 and SPH=1

The transfer signal sequence for Freescale SPI format with SPO=1 and SPH=1 is shown in Figure 12-9 on page 443, which covers both single and continuous transfers.

Figure 12-9. Freescale SPI Frame Format with SPO=1 and SPH=1

Note: Q is undefined.

In this configuration, during idle periods:

- SSIClk is forced High
- SSIFss is forced High
- The transmit data line SSITx is arbitrarily forced Low
- When the SSI is configured as a master, it enables the SSIClk pad
- When the SSI is configured as a slave, it disables the SSIClk pad

If the SSI is enabled and there is valid data within the transmit FIFO, the start of transmission is signified by the SSIFss master signal being driven Low. The master SSITx output pad is enabled. After a further one-half SSIClk period, both master and slave data are enabled onto their respective transmission lines. At the same time, SSIClk is enabled with a falling edge transition. Data is then captured on the rising edges and propagated on the falling edges of the SSIClk signal.

After all bits have been transferred, in the case of a single word transmission, the SSIFss line is returned to its idle high state one SSIClk period after the last bit has been captured.

For continuous back-to-back transmissions, the SSIFss pin remains in its active Low state, until the final bit of the last word has been captured, and then returns to its idle state as described above.

For continuous back-to-back transfers, the SSIFss pin is held Low between successive data words and termination is the same as that of the single word transfer.

#### **12.3.4.7 MICROWIRE Frame Format**

Figure 12-10 on page 443 shows the MICROWIRE frame format, again for a single frame. Figure 12-11 on page 444 shows the same format when back-to-back frames are transmitted.




Figure 12-10. MICROWIRE Frame Format (Single Frame)

November 18, 2011 443

MICROWIRE format is very similar to SPI format, except that transmission is half-duplex instead of full-duplex, using a master-slave message passing technique. Each serial transmission begins with an 8-bit control word that is transmitted from the SSI to the off-chip slave device. During this transmission, no incoming data is received by the SSI. After the message has been sent, the off-chip slave decodes it and, after waiting one serial clock after the last bit of the 8-bit control message has been sent, responds with the required data. The returned data is 4 to 16 bits in length, making the total frame length anywhere from 13 to 25 bits.

In this configuration, during idle periods:

- SSIClk is forced Low
- SSIFss is forced High
- The transmit data line SSITx is arbitrarily forced Low

A transmission is triggered by writing a control byte to the transmit FIFO. The falling edge of SSIFss causes the value contained in the bottom entry of the transmit FIFO to be transferred to the serial shift register of the transmit logic, and the MSB of the 8-bit control frame to be shifted out onto the SSITx pin. SSIFss remains Low for the duration of the frame transmission. The SSIRx pin remains tristated during this transmission.

The off-chip serial slave device latches each control bit into its serial shifter on the rising edge of each SSIClk. After the last bit is latched by the slave device, the control byte is decoded during a one clock wait-state, and the slave responds by transmitting data back to the SSI. Each bit is driven onto the SSIRx line on the falling edge of SSIClk. The SSI in turn latches each bit on the rising edge of SSIClk. At the end of the frame, for single transfers, the SSIFss signal is pulled High one clock period after the last bit has been latched in the receive serial shifter, which causes the data to be transferred to the receive FIFO.

**Note:** The off-chip slave device can tristate the receive line either on the falling edge of SSIClk after the LSB has been latched by the receive shifter, or when the SSIFss pin goes High.

For continuous transfers, data transmission begins and ends in the same manner as a single transfer. However, the SSIFss line is continuously asserted (held Low) and transmission of data occurs back-to-back. The control byte of the next frame follows directly after the LSB of the received data from the current frame. Each of the received values is transferred from the receive shifter on the falling edge of SSIClk, after the LSB of the frame has been latched into the SSI.




Figure 12-11. MICROWIRE Frame Format (Continuous Transfer)

In the MICROWIRE mode, the SSI slave samples the first bit of receive data on the rising edge of SSIClk after SSIFss has gone Low. Masters that drive a free-running SSIClk must ensure that the SSIFss signal has sufficient setup and hold margins with respect to the rising edge of SSIClk.

Figure 12-12 on page 445 illustrates these setup and hold time requirements. With respect to the SSIClk rising edge on which the first bit of receive data is to be sampled by the SSI slave, SSIFss must have a setup of at least two times the period of SSIClk on which the SSI operates. With respect to the SSIClk rising edge previous to this edge, SSIFss must have a hold of at least one SSIClk period.




Figure 12-12. MICROWIRE Frame Format, SSIFss Input Setup and Hold Requirements

# 12.4 Initialization and Configuration

To use the SSI, its peripheral clock must be enabled by setting the SSI bit in the **RCGC1** register. For each of the frame formats, the SSI is configured using the following steps:

- 1. Ensure that the SSE bit in the SSICR1 register is disabled before making any configuration changes.
- 2. Select whether the SSI is a master or slave:
  - **a.** For master operations, set the **SSICR1** register to 0x0000.0000.
  - **b.** For slave mode (output enabled), set the **SSICR1** register to 0x0000.0004.
  - c. For slave mode (output disabled), set the **SSICR1** register to 0x0000.000C.
- 3. Configure the clock prescale divisor by writing the **SSICPSR** register.
- **4.** Write the **SSICR0** register with the following configuration:
  - Serial clock rate (SCR)
  - Desired clock phase/polarity, if using Freescale SPI mode (SPH and SPO)
  - The protocol mode: Freescale SPI, TI SSF, MICROWIRE (FRF)
  - The data size (DSS)
- 5. Enable the SSI by setting the SSE bit in the SSICR1 register.

As an example, assume the SSI must be configured to operate with the following parameters:

- Master operation
- Freescale SPI mode (SPO=1, SPH=1)

- 1 Mbps bit rate
- 8 data bits

Assuming the system clock is 20 MHz, the bit rate calculation would be:

```
FSSIClk = FSysClk / (CPSDVSR * (1 + SCR))
1x106 = 20x106 / (CPSDVSR * (1 + SCR))
```

In this case, if CPSDVSR=2, SCR must be 9.

The configuration sequence would be as follows:

- 1. Ensure that the SSE bit in the SSICR1 register is disabled.
- 2. Write the **SSICR1** register with a value of 0x0000.0000.
- **3.** Write the **SSICPSR** register with a value of 0x0000.0002.
- **4.** Write the **SSICR0** register with a value of 0x0000.09C7.
- **5.** The SSI is then enabled by setting the SSE bit in the **SSICR1** register to 1.

# 12.5 Register Map

Table 12-3 on page 446 lists the SSI registers. The offset listed is a hexadecimal increment to the register's address, relative to that SSI module's base address:

■ SSI0: 0x4000.8000

Note that the SSI module clock must be enabled before the registers can be programmed (see page 210). There must be a delay of 3 system clocks after the SSI module clock is enabled before any SSI module registers are accessed.

**Note:** The SSI must be disabled (see the SSE bit in the **SSICR1** register) before any of the control registers are reprogrammed.

Table 12-3. SSI Register Map

Offset	Name	Type	Reset	Description	See page
0x000	SSICR0	R/W	0x0000.0000	SSI Control 0	448
0x004	SSICR1	R/W	0x0000.0000	SSI Control 1	450
800x0	SSIDR	R/W	0x0000.0000	SSI Data	452
0x00C	SSISR	RO	0x0000.0003	SSI Status	453
0x010	SSICPSR	R/W	0x0000.0000	SSI Clock Prescale	455
0x014	SSIIM	R/W	0x0000.0000	SSI Interrupt Mask	456
0x018	SSIRIS	RO	0x0000.0008	SSI Raw Interrupt Status	458
0x01C	SSIMIS	RO	0x0000.0000	SSI Masked Interrupt Status	459
0x020	SSIICR	W1C	0x0000.0000	SSI Interrupt Clear	460

Table 12-3. SSI Register Map (continued)

Offset	Name	Туре	Reset	Description	See page
0xFD0	SSIPeriphID4	RO	0x0000.0000	SSI Peripheral Identification 4	461
0xFD4	SSIPeriphID5	RO	0x0000.0000	SSI Peripheral Identification 5	462
0xFD8	SSIPeriphID6	RO	0x0000.0000	SSI Peripheral Identification 6	463
0xFDC	SSIPeriphID7	RO	0x0000.0000	SSI Peripheral Identification 7	464
0xFE0	SSIPeriphID0	RO	0x0000.0022	SSI Peripheral Identification 0	465
0xFE4	SSIPeriphID1	RO	0x0000.0000	SSI Peripheral Identification 1	466
0xFE8	SSIPeriphID2	RO	0x0000.0018	SSI Peripheral Identification 2	467
0xFEC	SSIPeriphID3	RO	0x0000.0001	SSI Peripheral Identification 3	468
0xFF0	SSIPCellID0	RO	0x0000.000D	SSI PrimeCell Identification 0	469
0xFF4	SSIPCellID1	RO	0x0000.00F0	SSI PrimeCell Identification 1	470
0xFF8	SSIPCellID2	RO	0x0000.0005	SSI PrimeCell Identification 2	471
0xFFC	SSIPCellID3	RO	0x0000.00B1	SSI PrimeCell Identification 3	472

# 12.6 Register Descriptions


The remainder of this section lists and describes the SSI registers, in numerical order by address offset.

# Register 1: SSI Control 0 (SSICR0), offset 0x000

SSICR0 is control register 0 and contains bit fields that control various functions within the SSI module. Functionality such as protocol mode, clock rate, and data size are configured in this register.

#### SSI Control 0 (SSICR0)

SSI0 base: 0x4000.8000 Offset 0x000 Type R/W, reset 0x0000.0000



Bit/Field	Name	Туре	Reset	Description
31:16	reserved	RO	0x00	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
15:8	SCR	R/W	0x0000	SSI Serial Clock Rate  The value SCR is used to generate the transmit and receive bit rate of the SSI. The bit rate is:  BR=FSSIClk/(CPSDVSR * (1 + SCR))  where CPSDVSR is an even value from 2-254 programmed in the SSICPSR register, and SCR is a value from 0-255.
7	SPH	R/W	0	SSI Serial Clock Phase This bit is only applicable to the Freescale SPI Format. The SPH control bit selects the clock edge that captures data and allows it to change state. It has the most impact on the first bit transmitted by either allowing or not allowing a clock transition before the first data capture edge.  When the SPH bit is 0, data is captured on the first clock edge transition. If SPH is 1, data is captured on the second clock edge transition.
6	SPO	R/W	0	SSI Serial Clock Polarity  This bit is only applicable to the Freescale SPI Format.  When the SPO bit is 0, it produces a steady state Low value on the SSIClk pin. If SPO is 1, a steady state High value is placed on the SSIClk pin when data is not being transferred.
5:4	FRF	R/W	0x0	SSI Frame Format Select The FRF values are defined as follows:  Value Frame Format

Value Frame Format

0x0 Freescale SPI Frame Format

Texas Instruments Synchronous Serial Frame Format

MICROWIRE Frame Format 0x2

Reserved 0x3

Bit/Field	Name	Туре	Reset	Description
3:0	DSS	R/W	0x00	SSI Data Size Select The DSS values are defined as follows:
				Value Data Size
				0x0-0x2 Reserved
				0x3 4-bit data
				0x4 5-bit data
				0x5 6-bit data
				0x6 7-bit data
				0x7 8-bit data
				0x8 9-bit data
				0x9 10-bit data
				0xA 11-bit data
				0xB 12-bit data
				0xC 13-bit data
				0xD 14-bit data
				0xE 15-bit data
				0xF 16-bit data

# Register 2: SSI Control 1 (SSICR1), offset 0x004

SSICR1 is control register 1 and contains bit fields that control various functions within the SSI module. Master and slave mode functionality is controlled by this register.


#### SSI Control 1 (SSICR1)

SSI0 base: 0x4000.8000

Dit/Eiold

Nomo

Offset 0x004 Type R/W, reset 0x0000.0000



Divrieiu	Name	туре	Reset	Description
31:4	reserved	RO	0x00	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
3	SOD	R/W	0	SSI Slave Mode Output Disable

Description

Dooot

This bit is relevant only in the Slave mode (MS=1). In multiple-slave systems, it is possible for the SSI master to broadcast a message to all slaves in the system while ensuring that only one slave drives data onto the serial output line. In such systems, the TXD lines from multiple slaves could be tied together. To operate in such a system, the SOD bit can be

The SOD values are defined as follows:

#### Value Description

SSI can drive SSITx output in Slave Output mode.

configured so that the SSI slave does not drive the SSITx pin.

SSI must not drive the SSITx output in Slave mode.

#### 2 R/W MS 0 SSI Master/Slave Select

This bit selects Master or Slave mode and can be modified only when SSI is disabled (SSE=0).

The MS values are defined as follows:

#### Value Description

- Device configured as a master.
- Device configured as a slave.

Name	Type	Reset	Description
SSE	R/W	0	SSI Synchronous Serial Port Enable Setting this bit enables SSI operation. The SSE values are defined as follows:  Value Description 0 SSI operation disabled.
			1 SSI operation enabled.
			<b>Note:</b> This bit must be set to 0 before any control registers are reprogrammed.
LBM	R/W	0	SSI Loopback Mode Setting this bit enables Loopback Test mode. The LBM values are defined as follows:
	SSE	SSE R/W	SSE R/W 0

Value Description

- 0 Normal serial port operation enabled.
- Output of the transmit serial shift register is connected internally to the input of the receive serial shift register.

### Register 3: SSI Data (SSIDR), offset 0x008

**Important:** This register is read-sensitive. See the register description for details.

**SSIDR** is the data register and is 16-bits wide. When **SSIDR** is read, the entry in the receive FIFO (pointed to by the current FIFO read pointer) is accessed. As data values are removed by the SSI receive logic from the incoming data frame, they are placed into the entry in the receive FIFO (pointed to by the current FIFO write pointer).

When **SSIDR** is written to, the entry in the transmit FIFO (pointed to by the write pointer) is written to. Data values are removed from the transmit FIFO one value at a time by the transmit logic. It is loaded into the transmit serial shifter, then serially shifted out onto the SSITX pin at the programmed bit rate.


When a data size of less than 16 bits is selected, the user must right-justify data written to the transmit FIFO. The transmit logic ignores the unused bits. Received data less than 16 bits is automatically right-justified in the receive buffer.

When the SSI is programmed for MICROWIRE frame format, the default size for transmit data is eight bits (the most significant byte is ignored). The receive data size is controlled by the programmer. The transmit FIFO and the receive FIFO are not cleared even when the SSE bit in the **SSICR1** register is set to zero. This allows the software to fill the transmit FIFO before enabling the SSI.

#### SSI Data (SSIDR)

SSI0 base: 0x4000.8000 Offset 0x008

Type R/W, reset 0x0000.0000



Bit/Field	Name	Туре	Reset	Description
31:16	reserved	RO	0x0000	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
15:0	DATA	R/W	0x0000	SSI Receive/Transmit Data

A read operation reads the receive FIFO. A write operation writes the transmit FIFO.

Software must right-justify data when the SSI is programmed for a data size that is less than 16 bits. Unused bits at the top are ignored by the transmit logic. The receive logic automatically right-justifies the data.


# Register 4: SSI Status (SSISR), offset 0x00C

**SSISR** is a status register that contains bits that indicate the FIFO fill status and the SSI busy status.

SSI Status (SSISR)

SSI0 base: 0x4000.8000 Offset 0x00C

Type RO, reset 0x0000.0003



Bit/Field	Name	Type	Reset	Description
31:5	reserved	RO	0x00	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
4	BSY	RO	0	SSI Busy Bit
				The BSY values are defined as follows:
				Value Description
				0 SSI is idle.
				SSI is currently transmitting and/or receiving a frame, or the transmit FIFO is not empty.
3	RFF	RO	0	SSI Receive FIFO Full
				The RFF values are defined as follows:
				Value Description
				0 Receive FIFO is not full.
				1 Receive FIFO is full.
2	RNE	RO	0	SSI Receive FIFO Not Empty
				The RNE values are defined as follows:
				Value Description
				0 Receive FIFO is empty.
				1 Receive FIFO is not empty.
1	TNF	RO	1	SSI Transmit FIFO Not Full
				The TNF values are defined as follows:
				Value Description

- Transmit FIFO is full. 0
- Transmit FIFO is not full.

Bit/Field	Name	Туре	Reset	Description
0	TFE	R0	1	SSI Transmit FIFO Empty The TFE values are defined as follows:
				Value Description
				0 Transmit FIFO is not empty.
				1 Transmit FIFO is empty.


# Register 5: SSI Clock Prescale (SSICPSR), offset 0x010

SSICPSR is the clock prescale register and specifies the division factor by which the system clock must be internally divided before further use.

The value programmed into this register must be an even number between 2 and 254. The least-significant bit of the programmed number is hard-coded to zero. If an odd number is written to this register, data read back from this register has the least-significant bit as zero.

#### SSI Clock Prescale (SSICPSR)

SSI0 base: 0x4000.8000 Offset 0x010 Type R/W, reset 0x0000.0000



Bit/Field	Name	Type	Reset	Description
31:8	reserved	RO	0x00	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
7:0	CPSDVSR	R/W	0x00	SSI Clock Prescale Divisor

This value must be an even number from 2 to 254, depending on the frequency of SSIC1k. The LSB always returns 0 on reads.


# Register 6: SSI Interrupt Mask (SSIIM), offset 0x014

The SSIIM register is the interrupt mask set or clear register. It is a read/write register and all bits are cleared to 0 on reset.

On a read, this register gives the current value of the mask on the relevant interrupt. A write of 1 to the particular bit sets the mask, enabling the interrupt to be read. A write of 0 clears the corresponding mask.

#### SSI Interrupt Mask (SSIIM)

SSI0 base: 0x4000.8000 Offset 0x014 Type R/W, reset 0x0000.0000



Bit/Field	Name	Type	Reset	Description
31:4	reserved	RO	0x00	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
3	TXIM	R/W	0	SSI Transmit FIFO Interrupt Mask
				The TXIM values are defined as follows:
				Value Description
				0 TX FIFO half-empty or less condition interrupt is masked.
				1 TX FIFO half-empty or less condition interrupt is not masked.
2	RXIM	R/W	0	SSI Receive FIFO Interrupt Mask
				The RXIM values are defined as follows:
				Value Description
				0 RX FIFO half-full or more condition interrupt is masked.
				1 RX FIFO half-full or more condition interrupt is not masked.
1	RTIM	R/W	0	SSI Receive Time-Out Interrupt Mask
				The RTIM values are defined as follows:

#### Value Description

- RX FIFO time-out interrupt is masked.
- RX FIFO time-out interrupt is not masked.

1 RX FIFO overrun interrupt is not masked.

Bit/Field	Name	Туре	Reset	Description
0	RORIM	R/W	0	SSI Receive Overrun Interrupt Mask The RORIM values are defined as follows:
				Value Description
				0 RX FIFO overrun interrupt is masked.


November 18, 2011 457

# Register 7: SSI Raw Interrupt Status (SSIRIS), offset 0x018

The SSIRIS register is the raw interrupt status register. On a read, this register gives the current raw status value of the corresponding interrupt prior to masking. A write has no effect.

SSI Raw Interrupt Status (SSIRIS)

SSI0 base: 0x4000.8000 Offset 0x018 Type RO, reset 0x0000.0008




Bit/Field	Name	Туре	Reset	Description
31:4	reserved	RO	0x00	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
3	TXRIS	RO	1	SSI Transmit FIFO Raw Interrupt Status Indicates that the transmit FIFO is half empty or less, when set.
2	RXRIS	RO	0	SSI Receive FIFO Raw Interrupt Status Indicates that the receive FIFO is half full or more, when set.
1	RTRIS	RO	0	SSI Receive Time-Out Raw Interrupt Status Indicates that the receive time-out has occurred, when set.
0	RORRIS	RO	0	SSI Receive Overrun Raw Interrupt Status Indicates that the receive FIFO has overflowed, when set.

# Register 8: SSI Masked Interrupt Status (SSIMIS), offset 0x01C

The **SSIMIS** register is the masked interrupt status register. On a read, this register gives the current masked status value of the corresponding interrupt. A write has no effect.

SSI Masked Interrupt Status (SSIMIS)

SSI0 base: 0x4000.8000 Offset 0x01C Type RO, reset 0x0000.0000




Bit/Field	Name	Type	Reset	Description
31:4	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
3	TXMIS	RO	0	SSI Transmit FIFO Masked Interrupt Status Indicates that the transmit FIFO is half empty or less, when set.
2	RXMIS	RO	0	SSI Receive FIFO Masked Interrupt Status Indicates that the receive FIFO is half full or more, when set.
1	RTMIS	RO	0	SSI Receive Time-Out Masked Interrupt Status Indicates that the receive time-out has occurred, when set.
0	RORMIS	RO	0	SSI Receive Overrun Masked Interrupt Status Indicates that the receive FIFO has overflowed, when set.

# Register 9: SSI Interrupt Clear (SSIICR), offset 0x020

The SSIICR register is the interrupt clear register. On a write of 1, the corresponding interrupt is cleared. A write of 0 has no effect.

#### SSI Interrupt Clear (SSIICR)

SSI0 base: 0x4000.8000 Offset 0x020 Type W1C, reset 0x0000.0000



Bit/Field	Name	Type	Reset	Description
31:2	reserved	RO	0x00	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should preserved across a read-modify-write operation.
1	RTIC	W1C	0	SSI Receive Time-Out Interrupt Clear The RTIC values are defined as follows:
				Value Description  0 No effect on interrupt.  1 Clears interrupt.
0	RORIC	W1C	0	SSI Receive Overrun Interrupt Clear The RORIC values are defined as follows:

Value Description

No effect on interrupt.

should be


Clears interrupt.

# Register 10: SSI Peripheral Identification 4 (SSIPeriphID4), offset 0xFD0

The SSIPeriphIDn registers are hard-coded and the fields within the register determine the reset value.

### SSI Peripheral Identification 4 (SSIPeriphID4)

SSI0 base: 0x4000.8000 Offset 0xFD0 Type RO, reset 0x0000.0000




Bit/Field	Name	Type	Reset	Description
31:8	reserved	RO	0x00	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
7:0	PID4	RO	0x00	SSI Peripheral ID Register[7:0]

# Register 11: SSI Peripheral Identification 5 (SSIPeriphID5), offset 0xFD4

The SSIPeriphIDn registers are hard-coded and the fields within the register determine the reset value.

#### SSI Peripheral Identification 5 (SSIPeriphID5)

SSI0 base: 0x4000.8000 Offset 0xFD4 Type RO, reset 0x0000.0000




Bit/Field	Name	Type	Reset	Description
31:8	reserved	RO	0x00	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
7:0	PID5	RO	0x00	SSI Peripheral ID Register[15:8]

### Register 12: SSI Peripheral Identification 6 (SSIPeriphID6), offset 0xFD8

The SSIPeriphIDn registers are hard-coded and the fields within the register determine the reset value.

### SSI Peripheral Identification 6 (SSIPeriphID6)

SSI0 base: 0x4000.8000 Offset 0xFD8 Type RO, reset 0x0000.0000




Bit/Field	Name	Type	Reset	Description
31:8	reserved	RO	0x00	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
7:0	PID6	RO	0x00	SSI Peripheral ID Register[23:16]

# Register 13: SSI Peripheral Identification 7 (SSIPeriphID7), offset 0xFDC

The SSIPeriphIDn registers are hard-coded and the fields within the register determine the reset value.

#### SSI Peripheral Identification 7 (SSIPeriphID7)

SSI0 base: 0x4000.8000 Offset 0xFDC Type RO, reset 0x0000.0000




Bit/Field	Name	Type	Reset	Description
31:8	reserved	RO	0x00	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
7:0	PID7	RO	0x00	SSI Peripheral ID Register[31:24]

### Register 14: SSI Peripheral Identification 0 (SSIPeriphID0), offset 0xFE0

The SSIPeriphIDn registers are hard-coded and the fields within the register determine the reset value.

### SSI Peripheral Identification 0 (SSIPeriphID0)

SSI0 base: 0x4000.8000 Offset 0xFE0 Type RO, reset 0x0000.0022




Bit/Field	Name	Type	Reset	Description
31:8	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
7:0	PID0	RO	0x22	SSI Peripheral ID Register[7:0]

# Register 15: SSI Peripheral Identification 1 (SSIPeriphID1), offset 0xFE4

The SSIPeriphIDn registers are hard-coded and the fields within the register determine the reset value.

SSI Peripheral Identification 1 (SSIPeriphID1)

SSI0 base: 0x4000.8000 Offset 0xFE4 Type RO, reset 0x0000.0000




Bit/Field	Name	Type	Reset	Description
31:8	reserved	RO	0x00	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
7:0	PID1	RO	0x00	SSI Peripheral ID Register [15:8]

# Register 16: SSI Peripheral Identification 2 (SSIPeriphID2), offset 0xFE8

The SSIPeriphIDn registers are hard-coded and the fields within the register determine the reset value.

### SSI Peripheral Identification 2 (SSIPeriphID2)

SSI0 base: 0x4000.8000 Offset 0xFE8 Type RO, reset 0x0000.0018




Bit/Field	Name	Type	Reset	Description
31:8	reserved	RO	0x00	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
7:0	PID2	RO	0x18	SSI Peripheral ID Register [23:16]

# Register 17: SSI Peripheral Identification 3 (SSIPeriphID3), offset 0xFEC

The SSIPeriphIDn registers are hard-coded and the fields within the register determine the reset value.

SSI Peripheral Identification 3 (SSIPeriphID3)

SSI0 base: 0x4000.8000 Offset 0xFEC Type RO, reset 0x0000.0001




Bit/Field	Name	Type	Reset	Description
31:8	reserved	RO	0x00	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
7:0	PID3	RO	0x01	SSI Peripheral ID Register [31:24]

## Register 18: SSI PrimeCell Identification 0 (SSIPCellID0), offset 0xFF0

The SSIPCellIDn registers are hard-coded, and the fields within the register determine the reset value.

## SSI PrimeCell Identification 0 (SSIPCellID0)

SSI0 base: 0x4000.8000 Offset 0xFF0 Type RO, reset 0x0000.000D




Bit/Field	Name	Type	Reset	Description
31:8	reserved	RO	0x00	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
7:0	CID0	RO	0x0D	SSI PrimeCell ID Register [7:0]

## Register 19: SSI PrimeCell Identification 1 (SSIPCellID1), offset 0xFF4

The SSIPCeIIIDn registers are hard-coded, and the fields within the register determine the reset value.

## SSI PrimeCell Identification 1 (SSIPCellID1)

SSI0 base: 0x4000.8000 Offset 0xFF4 Type RO, reset 0x0000.00F0




Bit/Field	Name	Type	Reset	Description
31:8	reserved	RO	0x00	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
7:0	CID1	RO	0xF0	SSI PrimeCell ID Register [15:8]

## Register 20: SSI PrimeCell Identification 2 (SSIPCellID2), offset 0xFF8

The SSIPCellIDn registers are hard-coded, and the fields within the register determine the reset value.

## SSI PrimeCell Identification 2 (SSIPCelIID2)

SSI0 base: 0x4000.8000 Offset 0xFF8 Type RO, reset 0x0000.0005




Bit/Field	Name	Type	Reset	Description
31:8	reserved	RO	0x00	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
7:0	CID2	RO	0x05	SSI PrimeCell ID Register [23:16]

## Register 21: SSI PrimeCell Identification 3 (SSIPCellID3), offset 0xFFC

The SSIPCeIIIDn registers are hard-coded, and the fields within the register determine the reset value.

## SSI PrimeCell Identification 3 (SSIPCellID3)

SSI0 base: 0x4000.8000 Offset 0xFFC Type RO, reset 0x0000.00B1



Bit/Field	Name	Type	Reset	Description
31:8	reserved	RO	0x00	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
7:0	CID3	RO	0xB1	SSI PrimeCell ID Register [31:24]

## 13 Ethernet Controller

The Stellaris<sup>®</sup> Ethernet Controller consists of a fully integrated media access controller (MAC) and network physical (PHY) interface. The Ethernet Controller conforms to *IEEE 802.3* specifications and fully supports 10BASE-T and 100BASE-TX standards.

The Stellaris Ethernet Controller module has the following features:

- Conforms to the *IEEE 802.3-2002 specification* 
  - 10BASE-T/100BASE-TX IEEE-802.3 compliant. Requires only a dual 1:1 isolation transformer interface to the line
  - 10BASE-T/100BASE-TX ENDEC, 100BASE-TX scrambler/descrambler
  - Full-featured auto-negotiation
- Multiple operational modes
  - Full- and half-duplex 100 Mbps
  - Full- and half-duplex 10 Mbps
  - Power-saving and power-down modes
- Highly configurable
  - Programmable MAC address
  - LED activity selection
  - Promiscuous mode support
  - CRC error-rejection control
  - User-configurable interrupts
- Physical media manipulation
  - Automatic MDI/MDI-X cross-over correction
  - Register-programmable transmit amplitude
  - Automatic polarity correction and 10BASE-T signal reception

## 13.1 Block Diagram

As shown in Figure 13-1 on page 474, the Ethernet Controller is functionally divided into two layers: the Media Access Controller (MAC) layer and the Network Physical (PHY) layer. These layers correspond to the OSI model layers 2 and 1. The CPU accesses the Ethernet Controller via the MAC layer. The MAC layer provides transmit and receive processing for Ethernet frames. The MAC layer also provides the interface to the PHY layer via an internal Media Independent Interface (MII). The PHY layer communicates with the Ethernet bus.

Figure 13-1. Ethernet Controller





Figure 13-2 on page 474 shows more detail of the internal structure of the Ethernet Controller and how the register set relates to various functions.

Figure 13-2. Ethernet Controller Block Diagram



## 13.2 Signal Description

Table 13-1 on page 475 and Table 13-2 on page 475 list the external signals of the Ethernet Controller and describe the function of each. The Ethernet LED signals are alternate functions for GPIO signals and default to be GPIO signals at reset. The column in the table below titled "Pin Assignment" lists the GPIO pin placement for the LED signals. The AFSEL bit in the **GPIO Alternate Function Select (GPIOAFSEL)** register (page 272) should be set to choose the LED function. For more information on configuring GPIOs, see "General-Purpose Input/Outputs (GPIOs)" on page 251. The remaining signals (with the word "fixed" in the Pin Mux/Pin Assignment column) have a fixed pin assignment and function.

Table 13-1. Ethernet Signals (100LQFP)

Pin Name	Pin Number	Pin Type	Buffer Type <sup>a</sup>	Description
ERBIAS	41	I	Analog	12.4-kΩ resistor (1% precision) used internally for Ethernet PHY.
GNDPHY	42 85 86	-	Power	GND of the Ethernet PHY.
LED0	59	0	TTL	Ethernet LED 0.
LED1	60	0	TTL	Ethernet LED 1.
MDIO	58	I/O	TTL	MDIO of the Ethernet PHY.
RXIN	37	I	Analog	RXIN of the Ethernet PHY.
RXIP	40	I	Analog	RXIP of the Ethernet PHY.
TXON	46	0	Analog	TXON of the Ethernet PHY.
TXOP	43	0	Analog	TXOP of the Ethernet PHY.
VCCPHY	36 83 84	-	Power	VCC of the Ethernet PHY.
XTALNPHY	17	0	TTL	Ethernet PHY XTALN 25-MHz oscillator crystal output. Leave unconnected when using a single-ended 25-MHz clock input connected to the XTALPPHY pin.
XTALPPHY	16	I	TTL	Ethernet PHY XTALP 25-MHz oscillator crystal input or external clock reference input.

a. The TTL designation indicates the pin has TTL-compatible voltage levels.

Table 13-2. Ethernet Signals (108BGA)

Pin Name	Pin Number	Pin Type	Buffer Type <sup>a</sup>	Description
ERBIAS	К3	I	Analog	12.4-k $\Omega$ resistor (1% precision) used internally for Ethernet PHY.
GNDPHY	C8 C9 K4	-	Power	GND of the Ethernet PHY.
LED0	J12	0	TTL	Ethernet LED 0.
LED1	J11	0	TTL	Ethernet LED 1.
MDIO	L9	I/O	TTL	MDIO of the Ethernet PHY.
RXIN	L7	I	Analog	RXIN of the Ethernet PHY.
RXIP	M7	1	Analog	RXIP of the Ethernet PHY.
TXON	L8	0	Analog	TXON of the Ethernet PHY.
TXOP	M8	0	Analog	TXOP of the Ethernet PHY.
VCCPHY	C10 D10 D11	-	Power	VCC of the Ethernet PHY.
XTALNPHY	J1	0	TTL	Ethernet PHY XTALN 25-MHz oscillator crystal output. Leave unconnected when using a single-ended 25-MHz clock input connected to the XTALPPHY pin.
XTALPPHY	J2	ļ	TTL	Ethernet PHY XTALP 25-MHz oscillator crystal input or external clock reference input.

a. The TTL designation indicates the pin has TTL-compatible voltage levels.

## 13.3 Functional Description

Note: A 12.4-k $\Omega$  resistor should be connected between the ERBIAS and ground. The 12.4-k $\Omega$  resistor should have a 1% tolerance and should be located in close proximity to the ERBIAS pin. Power dissipation in the resistor is low, so a chip resistor of any geometry may be used.

The functional description of the Ethernet Controller is discussed in the following sections.


## 13.3.1 MAC Operation

The following sections decribe the operation of the MAC unit, including an overview of the Ethernet frame format, the MAC layer FIFOs, Ethernet transmission and reception options, and LED indicators.

#### 13.3.1.1 Ethernet Frame Format

Ethernet data is carried by Ethernet frames. The basic frame format is shown in Figure 13-3 on page 476.

Figure 13-3. Ethernet Frame



The seven fields of the frame are transmitted from left to right. The bits within the frame are transmitted from least to most significant bit.

#### ■ Preamble

The Preamble field is used to synchronize with the received frame's timing. The preamble is 7 octets long.

#### Start Frame Delimiter (SFD)

The SFD field follows the preamble pattern and indicates the start of the frame. Its value is 1010.1011.

## ■ Destination Address (DA)

This field specifies destination addresses for which the frame is intended. The LSB (bit 16 of DA oct 1 in the frame, see Table 13-3 on page 478) of the DA determines whether the address is an individual (0), or group/multicast (1) address.

### Source Address (SA)

The source address field identifies the station from which the frame was initiated.

#### ■ Length/Type Field

The meaning of this field depends on its numeric value. This field can be interpreted as length or type code. The maximum length of the data field is 1500 octets. If the value of the Length/Type field is less than or equal to 1500 decimal, it indicates the number of MAC client data octets. If the value of this field is greater than or equal to 1536 decimal, then it is type interpretation. The meaning of the Length/Type field when the value is between 1500 and 1536 decimal is unspecified by the IEEE 802.3 standard. However, the Ethernet Controller assumes type interpretation if the

value of the Length/Type field is greater than 1500 decimal. The definition of the Type field is specified in the IEEE 802.3 standard. The first of the two octets in this field is most significant.

#### Data

The data field is a sequence of octets that is at least 46 in length, up to 1500 in length. Full data transparency is provided so any values can appear in this field. A minimum frame size of 46 octets is required to meet the IEEE standard. If the frame size is too small, the Ethernet Controller automatically appends extra bits (a pad), thus the pad can have a size of 0 to 46 octets. Data padding can be disabled by clearing the PADEN bit in the **Ethernet MAC Transmit Control** (MACTCTL) register.

For the Ethernet Controller, data sent/received can be larger than 1500 bytes without causing a Frame Too Long error. Instead, a FIFO overrun error is reported using the FOV bit in the **Ethernet MAC Raw Interrupt Status(MACRIS)** register when the frame received is too large to fit into the Ethernet Controller's 2K RAM.

### Frame Check Sequence (FCS)

The frame check sequence carries the cyclic redundancy check (CRC) value. The CRC is computed over the destination address, source address, length/type, and data (including pad) fields using the CRC-32 algorithm. The Ethernet Controller computes the FCS value one nibble at a time. For transmitted frames, this field is automatically inserted by the MAC layer, unless disabled by clearing the CRC bit in the **MACTCTL** register. For received frames, this field is automatically checked. If the FCS does not pass, the frame is not placed in the RX FIFO, unless the FCS check is disabled by clearing the BADCRC bit in the **MACRCTL** register.

## 13.3.1.2 MAC Layer FIFOs

The Ethernet Controller is capable of simultaneous transmission and reception. This feature is enabled by setting the DUPLEX bit in the **MACTCTL** register.

For Ethernet frame transmission, a 2 KB transmit FIFO is provided that can be used to store a single frame. While the *IEEE 802.3 specification* limits the size of an Ethernet frame's payload section to 1500 Bytes, the Ethernet Controller places no such limit. The full buffer can be used, for a payload of up to 2032 bytes (as the first 16 bytes in the FIFO are reserved for destination address, source address and length/type information).

For Ethernet frame reception, a 2-KB receive FIFO is provided that can be used to store multiple frames, up to a maximum of 31 frames. If a frame is received, and there is insufficient space in the RX FIFO, an overflow error is indicated using the FOV bit in the **MACRIS** register.

For details regarding the TX and RX FIFO layout, refer to Table 13-3 on page 478. Please note the following difference between TX and RX FIFO layout. For the TX FIFO, the Data Length field in the first FIFO word refers to the Ethernet frame data payload, as shown in the 5th to nth FIFO positions. For the RX FIFO, the Frame Length field is the total length of the received Ethernet frame, including the Length/Type bytes and the FCS bits.

If FCS generation is disabled by clearing the CRC bit in the **MACTCTL** register, the last word in the TX FIFO must contain the FCS bytes for the frame that has been written to the FIFO.

Also note that if the length of the data payload section is not a multiple of 4, the FCS field is not be aligned on a word boundary in the FIFO. However, for the RX FIFO the beginning of the next frame is always on a word boundary.

Table 13-3. TX & RX FIFO Organization

FIFO Word Read/Write Sequence	Word Bit Fields	TX FIFO (Write)	RX FIFO (Read)				
1st	7:0	Data Length Least Significant Byte	Frame Length Least Significant Byte				
	15:8	Data Length Most Significant Byte	Frame Length Most Significant Byte				
	23:16	DA	oct 1				
	31:24	DA	oct 2				
2nd	7:0	DA	oct 3				
	15:8	DA	oct 4				
	23:16	DA	oct 5				
	31:24	DA	oct 6				
3rd	7:0	SA	SA oct 1				
	15:8	SA	SA oct 2				
	23:16	SA	oct 3				
	31:24	SA	oct 4				
4th	7:0	SA	SA oct 5				
	15:8	SA	SA oct 6				
	23:16	Len/Type Most	Len/Type Most Significant Byte				
	31:24	Len/Type Least	Len/Type Least Significant Byte				
5th to nth	7:0	data	data oct n				
	15:8	data d	data oct n+1				
	23:16	data o	oct n+2				
	31:24	data o	oct n+3				
last	7:0	FC	S 1				
	15:8	FC	FCS 2				
	23:16	FC	FCS 3				
	31:24	FC	S 4				

**Note:** If the CRC bit in the **MACTCTL** register is clear, the FCS bytes must be written with the correct CRC. If the CRC bit is set, the Ethernet Controller automatically writes the FCS bytes.

### 13.3.1.3 Ethernet Transmission Options

At the MAC layer, the transmitter can be configured for both full-duplex and half-duplex operation by using the <code>DUPLEX</code> bit in the **MACTCTL** register.

The Ethernet Controller automatically generates and inserts the Frame Check Sequence (FCS) at the end of the transmit frame when the CRC bit in the **MACTCTL** register is set. However, for test purposes, this feature can be disabled in order to generate a frame with an invalid CRC by clearing the CRC bit.

The *IEEE 802.3 specification* requires that the Ethernet frame payload section be a minimum of 46 bytes. The Ethernet Controller automatically pads the data section if the payload data section loaded into the FIFO is less than the minimum 46 bytes when the PADEN bit in the **MACTCTL** register is set. This feature can be disabled by clearing the PADEN bit.

The transmitter must be enabled by setting the TXEN bit in the TCTL register.

### 13.3.1.4 Ethernet Reception Options

The Ethernet Controller RX FIFO should be cleared during software initialization. The receiver should first be disabled by clearing the RXEN bit in the **Ethernet MAC Receive Control (MACRCTL)** register, then the FIFO can be cleared by setting the RSTFIFO bit in the **MACRCTL** register.

The receiver automatically rejects frames that contain bad CRC values in the FCS field. In this case, a Receive Error interrupt is generated and the receive data is lost. To accept all frames, clear the BADCRC bit in the **MACRCTL** register.

In normal operating mode, the receiver accepts only those frames that have a destination address that matches the address programmed into the **Ethernet MAC Individual Address 0 (MACIA0)** and **Ethernet MAC Individual Address 1 (MACIA1)** registers. However, the Ethernet receiver can also be configured for Promiscuous and Multicast modes by setting the PRMS and AMUL bits in the **MACRCTL** register.

## 13.3.2 Internal MII Operation

For the MII management interface to function properly, the MDIO signal must be connected through a 10k  $\Omega$  pull-up resistor to the +3.3 V supply. Failure to connect this pull-up resistor prevents management transactions on this internal MII to function. Note that it is possible for data transmission across the MII to still function since the PHY layer auto-negotiates the link parameters by default.

For the MII management interface to function properly, the internal clock must be divided down from the system clock to a frequency no greater than 2.5 MHz. The **Ethernet MAC Management Divider (MACMDV)** register contains the divider used for scaling down the system clock. See page 498 for more details about the use of this register.

## 13.3.3 PHY Operation

The Physical Layer (PHY) in the Ethernet Controller includes integrated ENDECs, scrambler/descrambler, dual-speed clock recovery, and full-featured auto-negotiation functions. The transmitter includes an on-chip pulse shaper and a low-power line driver. The receiver has an adaptive equalizer and a baseline restoration circuit required for accurate clock and data recovery. The transceiver interfaces to Category-5 unshielded twisted pair (Cat-5 UTP) cabling for 100BASE-TX applications, and Category-3 unshielded twisted pair (Cat-3 UTP) for 10BASE-T applications. The Ethernet Controller is connected to the line media via dual 1:1 isolation transformers. No external filter is required.

### 13.3.3.1 Clock Selection

The Ethernet Controller has an on-chip crystal oscillator which can also be driven by an external oscillator. In this mode of operation, a 25-MHz crystal should be connected between the XTALPPHY and XTALNPHY pins. Alternatively, an external 25-MHz clock input can be connected to the XTALPPHY pin. In this mode of operation, a crystal is not required and the XTALNPHY pin must be tied to ground.

### 13.3.3.2 Auto-Negotiation

The Ethernet Controller supports the auto-negotiation functions of Clause 28 of the *IEEE 802.3* standard for 10/100 Mbps operation over copper wiring. This function is controlled via register settings. The auto-negotiation function is turned on by default, and the ANEGEN bit in the **Ethernet PHY Management Register 0 - Control (MR0)** is set after reset. Software can disable the auto-negotiation function by clearing the ANEGEN bit. The contents of the **Ethernet PHY Management Register - Auto-Negotiation Advertisement (MR4)** are reflected to the Ethernet Controller's link partner during auto-negotiation via fast-link pulse coding.

Once auto-negotiation is complete, the DPLX and RATE bits in the **Ethernet PHY Management Register 18 - Diagnostic (MR18)** register reflect the actual speed and duplex condition. If auto-negotiation fails to establish a link for any reason, the ANEGF bit in the **MR18** register reflects this and auto-negotiation restarts from the beginning. Setting the RANEG bit in the **MR0** register also causes auto-negotiation to restart.

### 13.3.3.3 Polarity Correction

The Ethernet Controller is capable of either automatic or manual polarity reversal for 10BASE-T and auto-negotiation functions. Bits 4 and 5 (RVSPOL and APOL) in the **Ethernet PHY Management Register 16 - Vendor-Specific (MR16)** control this feature. The default is automatic mode, where APOL is clear and RVSPOL indicates if the detection circuitry has inverted the input signal. To enter manual mode, APOL should be set. In manual mode RVSPOL controls the signal polarity.

### 13.3.3.4 MDI/MDI-X Configuration

The Ethernet Controller supports the MDI/MDI-X configuration as defined in *IEEE 802.3-2002* specification. The MDI/MDI-X configuration eliminates the need for cross-over cables when connecting to another device, such as a hub. The algorithm is controlled via settings in the **Ethernet PHY Management Register 24 - MDI/MIDIX Control (MR24)**. Refer to page 520 for additional details about these settings.

### 13.3.3.5 Power Management

The PHY has two power-saving modes:

- Power-Down
- Receive Power Management

Power-down mode is activated by setting the PWRDN bit in the **MR0** register. When the PHY is in power-down mode, it consumes minimum power. While in the power-down state, the Ethernet Controller still responds to management transactions.

Receive power management (RXCC mode) is activated by setting the RXCC bit in the **MR16** register. In this mode of operation, the adaptive equalizer, the clock recovery phase lock loop (PLL), and all other receive circuitry are powered down. As soon as a valid signal is detected, all circuits are automatically powered up to resume normal operation. Note that the RXCC mode is not supported during 10BASE-T operation.

#### 13.3.3.6 LED Indicators

The Ethernet Controller supports two LED signals that can be used to indicate various states of operation. These signals are mapped to the LED0 and LED1 pins. By default, these pins are configured as GPIO signals (PF3 and PF2). For the PHY layer to drive these signals, they must be reconfigured to their alternate function. See "General-Purpose Input/Outputs (GPIOs)" on page 251 for additional details. The function of these pins is programmable via the PHY layer **Ethernet PHY Management Register 23 - LED Configuration (MR23)**. Refer to page 519 for additional details on how to program these LED functions.

## 13.3.4 Interrupts

The Ethernet Controller can generate an interrupt for one or more of the following conditions:

A frame has been received into an empty RX FIFO

- A frame transmission error has occurred
- A frame has been transmitted successfully
- A frame has been received with inadequate room in the RX FIFO (overrun)
- A frame has been received with one or more error conditions (for example, FCS failed)
- An MII management transaction between the MAC and PHY layers has completed
- One or more of the following PHY layer conditions occurs:
  - Auto-Negotiate Complete
  - Remote Fault
  - Link Status Change
  - Link Partner Acknowledge
  - Parallel Detect Fault
  - Page Received
  - Receive Error
  - Jabber Event Detected

## 13.4 Initialization and Configuration

The following sections describe the hardware and software configuration required to set up the Ethernet Controller.

## 13.4.1 Hardware Configuration

Figure 13-4 on page 482 shows the proper method for interfacing the Ethernet Controller to a 10/100BASE-T Ethernet jack.




Figure 13-4. Interface to an Ethernet Jack

The following isolation transformers have been tested and are known to successfully interface to the Ethernet PHY layer.

- Isolation Transformers
  - TDK TLA-6T103
  - Bel-Fuse S558-5999-46
  - Halo TG22-3506ND
  - Pulse PE-68515
  - Valor ST6118
  - YCL 20PMT04
- Isolation transformers in low profile packages (0.100 in/2.5 mm or less)
  - TDK TLA-6T118
  - Halo TG110-S050
  - PCA EPF8023G
- Isolation transformers with integrated RJ45 connector
  - TDK TLA-6T704
  - Delta RJS-1A08T089A
- Isolation transformers with integrated RJ45 connector, LEDs and termination resistors
  - Pulse J0011D21B/E
  - Pulse J3011G21DNL

## 13.4.2 Software Configuration

To use the Ethernet Controller, it must be enabled by setting the EPHY0 and EMAC0 bits in the **RCGC2** register (see page 216). The following steps can then be used to configure the Ethernet Controller for basic operation.

- 1. Program the **MACDIV** register to obtain a 2.5 MHz clock (or less) on the internal MII. Assuming a 20-MHz system clock, the **MACDIV** value should be 0x03 or greater.
- 2. Program the MACIA0 and MACIA1 register for address filtering.
- **3.** Program the **MACTCTL** register for Auto CRC generation, padding, and full-duplex operation using a value of 0x16.

- **4.** Program the **MACRCTL** register to flush the receive FIFO and reject frames with bad FCS using a value of 0x18.
- **5.** Enable both the Transmitter and Receive by setting the LSB in both the **MACTCTL** and **MACRCTL** registers.
- 6. To transmit a frame, write the frame into the TX FIFO using the **Ethernet MAC Data (MACDATA)** register. Then set the NEWTX bit in the **Ethernet Mac Transmission Request (MACTR)** register to initiate the transmit process. When the NEWTX bit has been cleared, the TX FIFO is available for the next transmit frame.
- 7. To receive a frame, wait for the NPR field in the Ethernet MAC Number of Packets (MACNP) register to be non-zero. Then begin reading the frame from the RX FIFO by using the MACDATA register. To ensure that the entire packet is received, either use the DriverLib EthernetPacketGet() API or compare the number of bytes received to the Length field from the frame to determine when the packet has been completely read.

## 13.5 Ethernet Register Map

Table 13-4 on page 483 lists the Ethernet MAC registers. All addresses given are relative to the Ethernet MAC base address of 0x4004.8000. Note that the Ethernet module clock must be enabled before the registers can be programmed (see page 216). There must be a delay of 3 system clocks after the Ethernet module clock is enabled before any Ethernet module registers are accessed.

The IEEE 802.3 standard specifies a register set for controlling and gathering status from the PHY layer. The registers are collectively known as the MII Management registers and are detailed in Section 22.2.4 of the IEEE 802.3 specification. Table 13-4 on page 483 also lists these MII Management registers. All addresses given are absolute and are written directly to the REGADR field of the Ethernet MAC Management Control (MACMCTL) register. The format of registers 0 to 15 are defined by the IEEE specification and are common to all PHY layer implementations. The only variance allowed is for features that may or may not be supported by a specific PHY implementation. Registers 16 to 31 are vendor-specific registers, used to support features that are specific to a vendor's PHY implementation. Vendor-specific registers not listed are reserved.

Table 13-4. Ethernet Register Map

Offset	Name	Туре	Reset	Description	See page
Ethernet	MAC				
0x000	MACRIS/MACIACK	R/W1C	0x0000.0000	Ethernet MAC Raw Interrupt Status/Acknowledge	485
0x004	MACIM	R/W	0x0000.007F	Ethernet MAC Interrupt Mask	488
0x008	MACRCTL	R/W	0x0000.0008	Ethernet MAC Receive Control	489
0x00C	MACTCTL	R/W	0x0000.0000	Ethernet MAC Transmit Control	490
0x010	MACDATA	R/W	0x0000.0000	Ethernet MAC Data	491
0x014	MACIA0	R/W	0x0000.0000	Ethernet MAC Individual Address 0	493
0x018	MACIA1	R/W	0x0000.0000	Ethernet MAC Individual Address 1	494
0x01C	MACTHR	R/W	0x0000.003F	Ethernet MAC Threshold	495
0x020	MACMCTL	R/W	0x0000.0000	Ethernet MAC Management Control	497

Table 13-4. Ethernet Register Map (continued)

Offset	Name	Туре	Reset	Description	See page
0x024	MACMDV	R/W	0x0000.0080	Ethernet MAC Management Divider	498
0x02C	MACMTXD	R/W	0x0000.0000	Ethernet MAC Management Transmit Data	499
0x030	MACMRXD	R/W	0x0000.0000	Ethernet MAC Management Receive Data	500
0x034	MACNP	RO	0x0000.0000	Ethernet MAC Number of Packets	501
0x038	MACTR	R/W	0x0000.0000	Ethernet MAC Transmission Request	502
MII Manag	gement	1			
-	MR0	R/W	0x3100	Ethernet PHY Management Register 0 – Control	503
-	MR1	RO	0x7849	Ethernet PHY Management Register 1 – Status	505
-	MR2	RO	0x000E	Ethernet PHY Management Register 2 – PHY Identifier 1	507
-	MR3	RO	0x7237	Ethernet PHY Management Register 3 – PHY Identifier 2	508
-	MR4	R/W	0x01E1	Ethernet PHY Management Register 4 – Auto-Negotiation Advertisement	509
-	MR5	RO	0x0000	Ethernet PHY Management Register 5 – Auto-Negotiation Link Partner Base Page Ability	511
-	MR6	RO	0x0000	Ethernet PHY Management Register 6 – Auto-Negotiation Expansion	512
-	MR16	R/W	0x0140	Ethernet PHY Management Register 16 – Vendor-Specific	513
-	MR17	R/W	0x0000	Ethernet PHY Management Register 17 – Interrupt Control/Status	515
-	MR18	RO	0x0000	Ethernet PHY Management Register 18 – Diagnostic	517
-	MR19	R/W	0x4000	Ethernet PHY Management Register 19 – Transceiver Control	518
-	MR23	R/W	0x0010	Ethernet PHY Management Register 23 – LED Configuration	519
-	MR24	R/W	0x00C0	Ethernet PHY Management Register 24 –MDI/MDIX Control	520

## 13.6 Ethernet MAC Register Descriptions

The remainder of this section lists and describes the Ethernet MAC registers, in numerical order by address offset. Also see "MII Management Register Descriptions" on page 502.

## Register 1: Ethernet MAC Raw Interrupt Status/Acknowledge (MACRIS/MACIACK), offset 0x000


The MACRIS/MACIACK register is the interrupt status and acknowledge register. On a read, this register gives the current status value of the corresponding interrupt prior to masking. On a write, setting any bit clears the corresponding interrupt status bit.

### Reads

Ethernet MAC Raw Interrupt Status/Acknowledge (MACRIS/MACIACK)

Base 0x4004.8000

Offset 0x000 Type RO, reset 0x0000.0000




set	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0
В	it/Field		Name Type Reset				Desc	ription								
	31:7		reserved RO		0x0000.00	comp	Software should not rely on the value of a reserved bit. To p compatibility with future products, the value of a reserved bit preserved across a read-modify-write operation.						•			
	6		PHYII	NT	R	0	0	O PHY Interrupt When set, indicates th occurred. <b>MR17</b> in the event that triggered thi				nust be re			•	
	5		MDIN	NT	R	0	0	MII Transaction Complete When set, indicates that a transa has completed successfully.				nsaction	(read or v	write) on	the MII i	nterface
	4		RXE	:R	R	0	0	This I		ates that		r was en e this int				r. The
									receivenly).	e error o	ccurs du	iring the	receptio	n of a fra	ame (100	) Mb/s
									he fram		an integ	er numbe	er of byte	es (dribb	le bits) d	ue to an
								■ T	he CR0	C of the f	frame do	es not p	ass the I	FCS che	ck.	
										ith/type f ed as a l		consiste eld.	nt with th	ne frame	data siz	e when
	3		FO\	V	R	0	0	FIFO	Overru	n						
								Wher FIFO	,	dicates t	that an c	verrun w	as enco	untered	on the re	eceive

Bit/Field	Name	Туре	Reset	Description
2	TXEMP	RO	0	Transmit FIFO Empty When set, indicates that the packet was transmitted and that the TX FIFO is empty.
1	TXER	RO	0	Transmit Error When set, indicates that an error was encountered on the transmitter. The possible errors that can cause this interrupt bit to be set are:  The data length field stored in the TX FIFO exceeds 2032 decimal (buffer length - 16 bytes of header data). The frame is not sent when this error occurs.  The retransmission attempts during the backoff process have exceeded the maximum limit of 16 decimal.
0	RXINT	RO	0	Packet Received  When set, indicates that at least one packet has been received and is stored in the receiver FIFO.

### Writes

Ethernet MAC Raw Interrupt Status/Acknowledge (MACRIS/MACIACK)

Base 0x4004.8000 Offset 0x000 Type WO, reset 0x0000.0000



Bit/Field	Name	Туре	Reset	Description
31:7	reserved	RO	0x0000.00	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
6	PHYINT	W1C	0	Clear PHY Interrupt Setting this bit clears the PHYINT interrupt in the MACRIS register.
5	MDINT	W1C	0	Clear MII Transaction Complete Setting this bit clears the MDINT interrupt in the MACRIS register.
4	RXER	W1C	0	Clear Receive Error Setting this bit clears the RXER interrupt in the MACRIS register.
3	FOV	W1C	0	Clear FIFO Overrun Setting this bit clears the FOV interrupt in the MACRIS register.


Bit/Field	Name	Туре	Reset	Description
2	TXEMP	W1C	0	Clear Transmit FIFO Empty Setting this bit clears the TXEMP interrupt in the <b>MACRIS</b> register.
1	TXER	W1C	0	Clear Transmit Error  Setting this bit clears the TXER interrupt in the MACRIS register and resets the TX FIFO write pointer.
0	RXINT	W1C	0	Clear Packet Received  Setting this bit clears the RXINT interrupt in the MACRIS register.

## Register 2: Ethernet MAC Interrupt Mask (MACIM), offset 0x004

This register allows software to enable/disable Ethernet MAC interrupts. Clearing a bit disables the interrupt, while setting the bit enables it.

## Ethernet MAC Interrupt Mask (MACIM)

Base 0x4004.8000 Offset 0x004 Type R/W, reset 0x0000.007F



Bit/Field	Name	Туре	Reset	Description
31:7	reserved	RO	0x0000.00	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
6	PHYINTM	R/W	1	Mask PHY Interrupt
				Clearing this bit masks the ${\tt PHYINT}$ bit in the MACRIS register from being set.
5	MDINTM	R/W	1	Mask MII Transaction Complete
				Clearing this bit masks the ${\tt MDINT}$ bit in the $\textbf{MACRIS}$ register from being set.
4	RXERM	R/W	1	Mask Receive Error
				Clearing this bit masks the ${\tt RXER}$ bit in the $\textbf{MACRIS}$ register from being set.
3	FOVM	R/W	1	Mask FIFO Overrun
				Clearing this bit masks the ${\tt FOV}$ bit in the $\textbf{MACRIS}$ register from being set.
2	TXEMPM	R/W	1	Mask Transmit FIFO Empty
				Clearing this bit masks the $\mathtt{TXEMP}$ bit in the $\textbf{MACRIS}$ register from being set.
1	TXERM	R/W	1	Mask Transmit Error
				Clearing this bit masks the $\mathtt{TXER}$ bit in the $\textbf{MACRIS}$ register from being set.
0	RXINTM	R/W	1	Mask Packet Received
				Clearing this bit masks the ${\tt RXINT}$ bit in the $\textbf{MACRIS}$ register from being set.

## Register 3: Ethernet MAC Receive Control (MACRCTL), offset 0x008


This register configures the receiver and controls the types of frames that are received.

It is important to note that when the receiver is enabled, all valid frames with a broadcast address of FF-FF-FF-FF-FF in the Destination Address field are received and stored in the RX FIFO, even if the AMUL bit is not set.

### Ethernet MAC Receive Control (MACRCTL)

Base 0x4004.8000 Offset 0x008

Type R/W, reset 0x0000.0008



Bit/Field	Name	Type	Reset	Description
31:5	reserved	RO	0x0000.000	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
4	RSTFIFO	R/W	0	Clear Receive FIFO
				When set, this bit clears the receive FIFO. This should be done when software initialization is performed.
				It is recommended that the receiver be disabled (RXEN = 0), before a reset is initiated (RSTFIFO = 1). This sequence flushes and resets the RX FIFO.
				This bit is automatically cleared when read.
3	BADCRC	R/W	1	Enable Reject Bad CRC
				When set, the BADCRC bit enables the rejection of frames with an incorrectly calculated CRC. If a bad CRC is encountered, the RXER bit in the <b>MACRIS</b> register is set and the receiver FIFO is reset.
2	PRMS	R/W	0	Enable Promiscuous Mode
				When set, the ${\tt PRMS}$ bit enables Promiscuous mode, which accepts all valid frames, regardless of the specified Destination Address.
1	AMUL	R/W	0	Enable Multicast Frames
				When set, the ${\tt AMUL}$ bit enables the reception of multicast frames.
0	RXEN	R/W	0	Enable Receiver
				When set the RXEN bit enables the Ethernet receiver. When this bit is clear, the receiver is disabled and all frames are ignored.


## Register 4: Ethernet MAC Transmit Control (MACTCTL), offset 0x00C

This register configures the transmitter and controls the frames that are transmitted.

Ethernet MAC Transmit Control (MACTCTL)

Base 0x4004.8000

Offset 0x00C Type R/W, reset 0x0000.0000



Bit/Field	Name	Туре	Reset	Description
31:5	reserved	RO	0x0000.000	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
4	DUPLEX	R/W	0	Enable Duplex Mode
				When set, this bit enables Duplex mode, allowing simultaneous transmission and reception.
3	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
2	CRC	R/W	0	Enable CRC Generation
				When set this bit enables the automatic generation of the CRC and its placement at the end of the packet. If this bit is clear, the frames placed in the TX FIFO are sent exactly as they are written into the FIFO.
				Note that this bit should generally be set.
1	PADEN	R/W	0	Enable Packet Padding
				When set, this bit enables the automatic padding of packets that do not meet the minimum frame size.
				Note that this bit should generally be set.
0	TXEN	R/W	0	Enable Transmitter
				When set, this bit enables the transmitter. When this bit is clear, the transmitter is disabled.

## Register 5: Ethernet MAC Data (MACDATA), offset 0x010

**Important:** This register is read-sensitive. See the register description for details.

This register enables software to access the TX and RX FIFOs.

Reads from this register return the data stored in the RX FIFO from the location indicated by the read pointer. The read pointer is then auto incremented to the next RX FIFO location. Reading from the RX FIFO when a frame has not been received or is in the process of being received will return indeterminate data and not increment the read pointer.


Writes to this register store the data in the TX FIFO at the location indicated by the write pointer. The write pointer is the auto incremented to the next TX FIFO location. Writing more data into the TX FIFO than indicated in the length field will result in the data being lost. Writing less data into the TX FIFO than indicated in the length field will result in indeterminate data being appended to the end of the frame to achieve the indicated length. Attempting to write the next frame into the TX FIFO before transmission of the first has completed will result in the data being lost.

There is no mechanism for randomly accessing bytes in either the RX or TX FIFOs. Data must be read from the RX FIFO sequentially and stored in a buffer for further processing. Once a read has been performed, the data in the FIFO cannot be re-read. Data must be written to the TX FIFO sequentially. If an error is made in placing the frame into the TX FIFO, the write pointer can be reset to the start of the TX FIFO by writing the TXER bit of the MACIACK register and then the data re-written.

#### Reads

### Ethernet MAC Data (MACDATA)

Base 0x4004.8000 Offset 0x010 Type RO, reset 0x0000.0000




The RXDATA bits represent the next word of data stored in the RX FIFO.

## Writes

## Ethernet MAC Data (MACDATA)

Base 0x4004.8000 Offset 0x010 Type WO, reset 0x0000.0000



Bit/Field	Name	Туре	Reset	Description
31:0	TXDATA	WO	0x0000 0000	Transmit FIFO Dat

The  $\ensuremath{\mathtt{TXDATA}}$  bits represent the next word of data to place in the TX FIFO for transmission.


## Register 6: Ethernet MAC Individual Address 0 (MACIA0), offset 0x014

This register enables software to program the first four bytes of the hardware MAC address of the Network Interface Card (NIC). (The last two bytes are in MACIA1). The 6-byte Individual Address is compared against the incoming Destination Address fields to determine whether the frame should be received.

### Ethernet MAC Individual Address 0 (MACIA0)

Base 0x4004.8000

Offset 0x014 Type R/W, reset 0x0000.0000



Bit/Field	Name	Type	Reset	Description
31:24	MACOCT4	R/W	0x00	MAC Address Octet 4
				The MACOCT4 bits represent the fourth octet of the MAC address used to uniquely identify the Ethernet Controller.
23:16	MACOCT3	R/W	0x00	MAC Address Octet 3
				The MACOCT3 bits represent the third octet of the MAC address used to uniquely identify the Ethernet Controller.
15:8	MACOCT2	R/W	0x00	MAC Address Octet 2
				The MACOCT2 bits represent the second octet of the MAC address used to uniquely identify the Ethernet Controller.
7:0	MACOCT1	R/W	0x00	MAC Address Octet 1

The MACOCT1 bits represent the first octet of the MAC address used to uniquely identify the Ethernet Controller.


## Register 7: Ethernet MAC Individual Address 1 (MACIA1), offset 0x018

This register enables software to program the last two bytes of the hardware MAC address of the Network Interface Card (NIC). (The first four bytes are in MACIAO). The 6-byte IAR is compared against the incoming Destination Address fields to determine whether the frame should be received.

Ethernet MAC Individual Address 1 (MACIA1)

Base 0x4004.8000

Offset 0x018
Type R/W, reset 0x0000.0000



Bit/Field	Name	Type	Reset	Description
31:16	reserved	RO	0x0000	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
15:8	MACOCT6	R/W	0x00	MAC Address Octet 6
				The MACOCT6 bits represent the sixth octet of the MAC address used to uniquely identify each Ethernet Controller.
7:0	MACOCT5	R/W	0x00	MAC Address Octet 5

The MACOCT5 bits represent the fifth octet of the MAC address used to uniquely identify the Ethernet Controller.

## Register 8: Ethernet MAC Threshold (MACTHR), offset 0x01C

In order to increase the transmission rate, it is possible to program the Ethernet Controller to begin transmission of the next frame prior to the completion of the transmission of the current frame. Note: Extreme care must be used when implementing this function. Software must be able to guarantee that the complete frame is able to be stored in the transmission FIFO prior to the completion of the transmission frame.

This register enables software to set the threshold level at which the transmission of the frame begins. If the THRESH bits are set to 0x3F, which is the reset value, the early transmission feature is disabled, and transmission does not start until the NEWTX bit is set in the **MACTR** register.

Writing the THRESH bits to any value besides 0x3F enables the early transmission feature. Once the byte count of data in the TX FIFO reaches the value derived from the THRESH bits as shown below, transmission of the frame begins. When THRESH is set to all 0s, transmission of the frame begins after 4 bytes (a single write) are stored in the TX FIFO. Each increment of the THRESH bit field waits for an additional 32 bytes of data (eight writes) to be stored in the TX FIFO. Therefore, a value of 0x01 causes the transmitter to wait for 36 bytes of data to be written while a value of 0x02 makes the wait equal to 68 bytes of written data. In general, early transmission starts when:

```
Number of Bytes >= 4 (THRESH x 8 + 1)
```


Reaching the threshold level has the same effect as setting the NEWTX bit in the **MACTR** register. Transmission of the frame begins and then the number of bytes indicated by the Data Length field is transmitted. Because under-run checking is not performed, if any event, such as an interrupt, delays the filling of the FIFO, the tail pointer may reach and pass the write pointer in the TX FIFO. In this event, indeterminate values are transmitted rather than the end of the frame. Therefore, sufficient bus bandwidth for writing to the TX FIFO must be guaranteed by the software.

If a frame smaller than the threshold level must be sent, the NEWTX bit in the **MACTR** register must be set with an explicit write. This initiates the transmission of the frame even though the threshold limit has not been reached.

If the threshold level is set too small, it is possible for the transmitter to underrun. If this occurs, the transmit frame is aborted, and a transmit error occurs. Note that in this case, the TXER bit in the MACRIS is not set meaning that the CPU receives no indication that a transmit error happened.

#### Ethernet MAC Threshold (MACTHR)

Base 0x4004.8000 Offset 0x01C



Bit/Field	Name	Туре	Reset	Description
5:0	THRESH	R/W	0x3F	Threshold Value  The THRESH bits represent the early transmit threshold. Once the amount of data in the TX FIFO exceeds the value represented by the above equation, transmission of the packet begins.

## Register 9: Ethernet MAC Management Control (MACMCTL), offset 0x020

This register enables software to control the transfer of data to and from the MII Management registers in the Ethernet PHY layer. The address, name, type, reset configuration, and functional description of each of these registers can be found in Table 13-4 on page 483 and in "MII Management Register Descriptions" on page 502.

In order to initiate a *read* transaction from the MII Management registers, the WRITE bit must be cleared during the same cycle that the START bit is set.

In order to initiate a *write* transaction to the MII Management registers, the WRITE bit must be set during the same cycle that the START bit is set.

### Ethernet MAC Management Control (MACMCTL)

Base 0x4004.8000 Offset 0x020

Type R/W, reset 0x0000.0000

_	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16
		1	1					rese	rved I		1		1	1		
Type	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO
Reset	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0
	15	14	13	12	11	10	9	8	7	6	5	4	3	2	1	0
		ı		rese	rved I						REGADR		ı	reserved	WRITE	START
Туре	RO	RO	RO	RO	RO	RO	RO	RO	R/W	R/W	R/W	R/W	R/W	RO	R/W	R/W
Reset	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0

Bit/Field	Name	Туре	Reset	Description
31:8	reserved	RO	0x0000.00	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
7:3	REGADR	R/W	0x0	MII Register Address
				The REGADR bit field represents the MII Management register address for the next MII management interface transaction. Refer to Table 13-4 on page 483 for the PHY register offsets.
				Note that any address that is not valid in the register map should not be written to and any data read should be ignored.
2	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
1	WRITE	R/W	0	MII Register Transaction Type
				The WRITE bit represents the operation of the next MII management interface transaction. If WRITE is set, the next operation is a write; if WRITE is clear, the next transaction is a read.
0	START	R/W	0	MII Register Transaction Enable
				The START bit represents the initiation of the next MII management interface transaction. When this bit is set, the MII register located at

REGADR is read (WRITE=0) or written (WRITE=1).

## Register 10: Ethernet MAC Management Divider (MACMDV), offset 0x024

This register enables software to set the clock divider for the Management Data Clock (MDC). This clock is used to synchronize read and write transactions between the system and the MII Management registers. The frequency of the MDC clock can be calculated from the following formula:


$$F_{mdc} = \frac{F_{ipclk}}{2 \times (MACDVR + 1)}$$

The clock divider must be written with a value that ensures that the MDC clock does not exceed a frequency of 2.5 MHz.

## Ethernet MAC Management Divider (MACMDV)

Base 0x4004.8000 Offset 0x024

Type R/W, reset 0x0000.0080



Bit/Field	Name	Type	Reset	Description
31:8	reserved	RO	0x0000.00	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
7:0	DIV	R/W	0x80	Clock Divider

The t DIV bits are used to set the clock divider for the MDC clock used to transmit data between the MAC and PHY layers over the serial MII interface.


## Register 11: Ethernet MAC Management Transmit Data (MACMTXD), offset 0x02C

This register holds the next value to be written to the MII Management registers.

### Ethernet MAC Management Transmit Data (MACMTXD)

Base 0x4004.8000

Offset 0x02C Type R/W, reset 0x0000.0000



Bit/Field	Name	Type	Reset	Description
31:16	reserved	RO	0x0000	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
15:0	MDTX	R/W	0x0000	MII Register Transmit Data

The  $\mathtt{MDTX}$  bits represent the data that will be written in the next  $\mathbf{MII}$ management transaction.


## Register 12: Ethernet MAC Management Receive Data (MACMRXD), offset 0x030

This register holds the last value read from the MII Management registers.

Ethernet MAC Management Receive Data (MACMRXD)

Base 0x4004.8000

Offset 0x030 Type R/W, reset 0x0000.0000



Bit/Field	Name	Type	Reset	Description
31:16	reserved	RO	0x0000	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
15:0	MDRX	R/W	0x0000	MII Register Receive Data

The  ${\tt MDRX}$  bits represent the data that was read in the previous  ${\tt MII}$ management transaction.


## Register 13: Ethernet MAC Number of Packets (MACNP), offset 0x034

This register holds the number of frames that are currently in the RX FIFO. When NPR is 0, there are no frames in the RX FIFO, and the RXINT bit is clear. When NPR is any other value, at least one frame is in the RX FIFO, and the RXINT bit in the **MACRIS** register is set.

Note: The FCS bytes are not included in the NPR value. As a result, the NPR value could be zero before the FCS bytes are read from the FIFO. In addition, a new packet could be received before the NPR value reaches zero. To ensure that the entire packet is received, either use the DriverLib EthernetPacketGet() API or compare the number of bytes received to the Length field from the frame to determine when the packet has been completely read.

Ethernet MAC Number of Packets (MACNP)

Base 0x4004.8000 Offset 0x034 Type RO, reset 0x0000.0000



Bit/Field	Name	Туре	Reset	Description
31:6	reserved	RO	0x0000.00	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
5:0	NPR	RO	0x00	Number of Packets in Receive FIFO

The NPR bits represent the number of packets stored in the RX FIFO. While the NPR field is greater than 0, the RXINT interrupt in the **MACRIS** register is set.


## Register 14: Ethernet MAC Transmission Request (MACTR), offset 0x038

This register enables software to initiate the transmission of the frame currently located in the TX FIFO. Once the frame has been transmitted from the TX FIFO or a transmission error has been encountered, the NEWTX bit is automatically cleared.

Ethernet MAC Transmission Request (MACTR)

Base 0x4004.8000 Offset 0x038

Type R/W, reset 0x0000.0000



Bit/Field	Name	Type	Reset	Description
31:1	reserved	RO	0x0000.000	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
0	NEWTX	R/W	0	New Transmission

When set, the NEWTX bit initiates an Ethernet transmission once the packet has been placed in the TX FIFO. This bit is cleared once the transmission has been completed. If early transmission is being used (see the **MACTHR** register), this bit does not need to be set.

## 13.7 MII Management Register Descriptions

The *IEEE 802.3 standard* specifies a register set for controlling and gathering status from the PHY layer. The registers are collectively known as the MII Management registers. All addresses given are absolute. Addresses not listed are reserved; these addresses should not be written to and any data read should be ignored. Also see "Ethernet MAC Register Descriptions" on page 484.

# Register 15: Ethernet PHY Management Register 0 – Control (MR0), address 0x00

This register enables software to configure the operation of the PHY layer. The default settings of these registers are designed to initialize the Ethernet Controller to a normal operational mode without configuration.

## Ethernet PHY Management Register 0 – Control (MR0)

Base 0x4004.8000 Address 0x00 Type R/W, reset 0x3100

	15	14	13	12	11	10	9	8	7	6	5	4	3	2	1	0
	RESET	LOOPBK	SPEEDSL	ANEGEN	PWRDN	ISO	RANEG	DUPLEX	COLT				reserved		1	
Type Reset	R/W 0	R/W 0	R/W 1	R/W 1	R/W 0	R/W 0	R/W 0	R/W 1	R/W 0	R/W 0	R/W 0	R/W 0	R/W 0	R/W 0	R/W 0	R/W 0
Е	Bit/Field		Nam	ne	Тур	oe	Reset	Des	cription							
	15		RES	ET	R/	W	0	Whe and	reinitiali	is bit res zes inter		machine	er register es. Once vare.			
	14		LOOF	РВК	R/	W	0	Whe igno		is bit ena			k mode o he data tl			
	13		SPEEI	DSL	R/	W	1			ription les the 1			f operation	•		X).
	12		ANEG	BEN	R/\	W	1		Ū	ation Ena		auto-ne	egotiation	proces	SS.	
	11		PWR	DN	R/	W	0	Whe		is bit pla	ces the f		er into a l	ow-pow	ver cons	uming
	10		ISC	)	R/	W	0		n set, th				t and rec		ta paths	and
	9		RANI	EG	R/	W	0	Whe	en set, th			-	jotiation p dware.	rocess.	. Once th	e restart

Bit/Field	Name	Туре	Reset	Description
8	DUPLEX	R/W	1	Set Duplex Mode
				Value Description
				Enables the Full-Duplex mode of operation. This bit can be set by software in a manual configuration process or by the auto-negotiation process.
				0 Enables the Half-Duplex mode of operation.
7	COLT	R/W	0	Collision Test
				When set, this bit enables the Collision Test mode of operation. The ${\tt COLT}$ bit is set after the initiation of a transmission and is cleared once the transmission is halted.
6:0	reserved	R/W	0x00	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.  These bits should always be written as zero.

3

ANEGA

RO

2

LINK

RO

JAB

RC

0

**EXTD** 

RO

### Register 16: Ethernet PHY Management Register 1 – Status (MR1), address 0x01

RO

6

MFPS

RO

5

ANEGC

RO

RFAULT

RC

When set, this bit indicates that the Management Interface is capable of receiving management frames with the preamble suppressed.

When set, this bit indicates that the auto-negotiation process has been

When set, this bit indicates that a remote fault condition has been detected. This bit remains set until it is read, even if the condition no

When set, this bit indicates that the Ethernet Controller has the ability

completed and that the extended registers defined by the

This register enables software to determine the capabilities of the PHY layer and perform its initialization and operation appropriately.

Ethernet PHY Management Register 1 – Status (MR1)

12

10T\_F

RO

11

10T\_H

RO

10

RO

reserved

RO

RO

13

100X H

RO

Base 0x4004.8000 Address 0x01 Type RO, reset 0x7849

14

100X F

RO

15

RO

5

4

3

**ANEGC** 

**RFAULT** 

ANEGA

RO

RC

RO

0

0

1

Туре

Reset	0 1	1	1	1	0	0	0	0	1	0	0	1	0	0	1
Bi	t/Field	Nam	е	Тур	ре	Reset	Desc	cription							
	15	reserv	red	R	0	0	com	ware sho patibility erved ac	with futu	ıre produ	icts, the	value of	a reserv	•	
	14	100X	_F	R	Э	1	100E	BASE-TX	(Full-Du	plex Mo	de				
								n set, thi orting 10					Controlle	is capal	ole of
	13	100X_	_H	R	Э	1	100E	BASE-TX	Half-Dι	ıplex Mo	de				
								n set, thi orting 10					Controlle	is capal	ole of
	12	10T_	F	R	Э	1	10B/	ASE-T F	ull-Duple	ex Mode					
								n set, thi ASE-T Fu				hernet C	Controlle	is capal	ole of
	11	10T_	Н	R	Э	1	10B/	ASE-T H	alf-Duple	ex Mode					
								n set, thi orting 10					Controlle	is capal	ole of
	10:7	reserv	red	R	0	0	com	ware sho patibility erved ac	with futu	ıre produ	icts, the	value of	a reserv	•	
	6	MFP	S	R	0	1	Man	agement	Frames	with Pre	eamble S	Suppress	sed		

**Auto-Negotiation Complete** 

Remote Fault

longer exists.

Auto-Negotiation

to perform auto-negotiation.

auto-negotiation protocol are valid.


Bit/Field	Name	Type	Reset	Description
2	LINK	RO	0	Link Made When set, this bit indicates that a valid link has been established by the Ethernet Controller.
1	JAB	RC	0	Jabber Condition  When set, this bit indicates that a jabber condition has been detected by the Ethernet Controller. This bit remains set until it is read, even if the jabber condition no longer exists.
0	EXTD	RO	1	Extended Capabilities  When set, this bit indicates that the Ethernet Controller provides an extended set of capabilities that can be accessed through the extended register set.

## Register 17: Ethernet PHY Management Register 2 – PHY Identifier 1 (MR2), address 0x02

This register, along with **MR3**, provides a 32-bit value indicating the manufacturer, model, and revision information.

Ethernet PHY Management Register 2 – PHY Identifier 1 (MR2)

Base 0x4004.8000 Address 0x02 Type RO, reset 0x000E




This field, along with the  $\mathtt{OUI}[5:0]$  field in MR3, makes up the Organizationally Unique Identifier indicating the PHY manufacturer.

## Register 18: Ethernet PHY Management Register 3 – PHY Identifier 2 (MR3), address 0x03

This register, along with **MR2**, provides a 32-bit value indicating the manufacturer, model, and revision information.

Ethernet PHY Management Register 3 – PHY Identifier 2 (MR3)

Base 0x4004.8000 Address 0x03 Type RO, reset 0x7237



Bit/Field	Name	Туре	Reset	Description
15:10	OUI[5:0]	RO	0x1C	Organizationally Unique Identifier[5:0]  This field, along with the OUI[21:6] field in MR2, makes up the Organizationally Unique Identifier indicating the PHY manufacturer.
9:4	MN	RO	0x23	Model Number The MN field represents the Model Number of the PHY.
3:0	RN	RO	0x7	Revision Number

The  ${\tt RN}$  field represents the Revision Number of the PHY implementation.

# Register 19: Ethernet PHY Management Register 4 – Auto-Negotiation Advertisement (MR4), address 0x04

This register provides the advertised abilities of the Ethernet Controller used during auto-negotiation. Bits 8:5 represent the Technology Ability Field bits. This field can be overwritten by software to auto-negotiate to an alternate common technology. Writing to this register has no effect until auto-negotiation is re-initiated by setting the RANEG bit in the **MR0** register.

Ethernet PHY Management Register 4 – Auto-Negotiation Advertisement (MR4)

Base 0x4004.8000 Address 0x04 Type R/W, reset 0x01E1

_	15	14	13	12	11	10	9	8	7	6	5	4	3	2	1	0					
	NP	reserved	RF		reser	ved		A3	A2	A1	A0			S	1	1					
Type Reset	RO 0	RO 0	R/W 0	RO 0	RO 0	RO 0	RO 0	R/W 1	R/W 1	R/W 1	R/W 1	RO 0	RO 0	RO 0	RO 0	RO 1					
В	it/Field		Nan	ne	Тур	oe .	Reset	Des	cription												
	15		NF	)	RO	)	0	Nex	t Page												
								Pag					net Conti iled inforr		•						
	14 reserved			ved	RO	)	0	com	npatibility	with fut	ure prod	ucts, the	ue of a reserved bit. To provide ne value of a reserved bit should be ite operation.								
	13		RF	:	RΛ	N	0	Remote Fault													
								When set, this bit indicates to the link partner that a Remote Fault condition has been encountered.													
	12:9	reserved			RO	)	0x0	com	npatibility	with fut		served bit. To provide of a reserved bit should be ion.									
	8		A3	}	RΛ	N	1	Technology Ability Field[3]													
								100 that	Base-TX this mod	( full-dup de is not	lex signa used, th	aling pro is bit car	thernet ( tocol. If so to be clea MR0 regi	oftware red and	wants to	ensure					
	7		A2	<u>!</u>	RΛ	N	1	Tecl	hnology	Ability Fi	eld[2]										
	/ A2						100 that	Base-TX this mod	et, this bit indicates that the Ethernet Controller supports the e-TX half-duplex signaling protocol. If software wants to ensure mode is not used, this bit can be cleared and auto-negotiation ed with the RANEG bit in the <b>MR0</b> register.												
	6		A1		RΛ	N	1	Tecl	hnology	Ability Fi	eld[1]										
						10B that	ASE-T for	ull-duple de is not	x signali used, th	ng proto is bit car	thernet ( col. If so n be clea MR0 regi	ftware w red and	ants to e	ensure							

Bit/Field	Name	Туре	Reset	Description
5	Α0	R/W	1	Technology Ability Field[0] When set, this bit indicates that the Ethernet Controller supports the 10BASE-T half-duplex signaling protocol. If software wants to ensure that this mode is not used, this bit can be cleared and auto-negotiation re-initiated with the RANEG bit in the MR0 register
4:0	S	RO	0x1	Selector Field  The S field encodes 32 possible messages for communicating between Ethernet Controllers. This field is hard-coded to 0x01, indicating that the Stellaris Ethernet Controller is <i>IEEE 802.3</i> compliant.

## Register 20: Ethernet PHY Management Register 5 – Auto-Negotiation Link Partner Base Page Ability (MR5), address 0x05

This register provides the advertised abilities of the link partner's Ethernet Controller that are received and stored during auto-negotiation.

Ethernet PHY Management Register 5 - Auto-Negotiation Link Partner Base Page Ability (MR5)

Base 0x4004.8000 Address 0x05 Type RO, reset 0x0000

14

13

S


RO

0x00

12

15

4:0



Selector Field

The  $\ensuremath{\mathtt{S}}$  field encodes possible messages for communicating between Ethernet Controllers.

Ethernet Controller. Refer to the IEEE 802.3 standard for definitions.

Value	Description
0x00	Reserved
0x01	IEEE Std 802.3
0x02	IEEE Std 802.9 ISLAN-16T
0x03	IEEE Std 802.5
0x04	IEEE Std 1394
0x05-0x1F	Reserved

## Register 21: Ethernet PHY Management Register 6 – Auto-Negotiation Expansion (MR6), address 0x06

This register enables software to determine the auto-negotiation and next page capabilities of the Ethernet Controller and the link partner after auto-negotiation.

Ethernet PHY Management Register 6 - Auto-Negotiation Expansion (MR6)


Base 0x4004.8000 Address 0x06 Type RO, reset 0x0000

0

**LPANEGA** 

RO

0



Link Partner is Auto-Negotiation Able
When set, this bit indicates that the link partner is enabled to support auto-negotiation.

When set, this bit indicates that a new page has been received from the link partner and stored. This bit remains set until the register is read.

# Register 22: Ethernet PHY Management Register 16 – Vendor-Specific (MR16), address 0x10

This register enables software to configure the operation of vendor-specific modes of the Ethernet Controller.

Ethernet PHY Management Register 16 – Vendor-Specific (MR16)

Base 0x4004.8000 Address 0x10 Type R/W, reset 0x0140

	15	14	13	12	11	10	9	8	7	6	5	4	3	2	1	0						
	RPTR	INPOL	reserved	TXHIM	SQEI	NL10	'	rese	rved	•	APOL	RVSPOL	rese	rved	PCSBP	RXCC						
Type Reset	R/W 0	R/W0 0	RO 0	R/W 0	R/W 0	R/W 0	RO 0	RO 1	RO 0	RO 1	R/W 0	R/W 0	RO 0	RO 0	R/W 0	R/W 0						
Е	Bit/Field		Nam	ie	Ту	ре	Reset	Des	cription													
	15		RPT	R	R/	W	0	Repeater Mode														
								full-d	When set, this bit enab full-duplex is not allow to receive activity.							-						
	14		INPO	DL	R/\	N0	0	Inte	rrupt Pol	arity												
								Valu	ue Desc	cription												
								1	Sets	the pola	rity of th	e PHY in	terrupt t	o be acti	ve High.							
								0	Sets	the pola	rity of th	e PHY in	terrupt t	o active	Low.							
								Important: Because the Media Access Controller expects active Low interrupts from the PHY, this bit must always be written with a 0 to ensure proper operation.														
	13		reserv	/ed	R	0	0	com	patibility	with futu	ıre prod	he value ucts, the dify-write	value of	a reserv								
	12		TXHI	M	R/	W	0	Trar	nsmit Hig	gh Imped	dance Mode											
								mod	le, the T	KOP and	rxon tra	the transmitter High Impedance mode. In this transmitter pins are put into a high impedance pins remain fully functional.										
	11		SQE	ΞI	R/	W	0	SQE	E Inhibit	Testing												
								Whe	en set, th	nis bit pro	hibits 1	0BASE-T	SQE te	sting.								
												s perform ne transm				on pulse						
	10		NL1	0	R/	W	0	Natu	ıral Loo	oback Mo	ode											
								this loop	When set, this bit enable this mode, the transmiss looped back onto the recenabled.			data rece	ived by t	he Ethe	rnet Con	troller is						
	9:6		reserv	ved	R	0	0x5	com	patibility	with futu	ıre prod	he value ucts, the dify-write	value of	a reserv	•							

Bit/Field	Name	Туре	Reset	Description
5	APOL	R/W	0	Auto-Polarity Disable When set, this bit disables the Ethernet Controller's auto-polarity function. If this bit is clear, the Ethernet Controller automatically inverts the received signal due to a wrong polarity connection during auto-negotiation when in 10BASE-T mode.
4	RVSPOL	R/W	0	Receive Data Polarity  This bit indicates whether the receive data pulses are being inverted. If the APOL bit is 0, then the RVSPOL bit is read-only and indicates whether the auto-polarity circuitry is reversing the polarity. In this case, if RVSPOL is set, it indicates that the receive data is inverted; if RVSPOL is clear, it indicates that the receive data is not inverted. If the APOL bit is 1, then the RVSPOL bit is writable and software can force the receive data to be inverted. Setting RVSPOL to 1 forces the receive data to be inverted; clearing RVSPOL does not invert the receive data.
3:2	reserved	RO	0x0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
1	PCSBP	R/W	0	PCS Bypass When set, this bit enables the bypass of the PCS and scrambling/descrambling functions in 100BASE-TX mode. This mode is only valid when auto-negotiation is disabled and 100BASE-TX mode is enabled.
0	RXCC	R/W	0	Receive Clock Control  When set, this bit enables the Receive Clock Control power saving mode if the Ethernet Controller is configured in 100BASE-TX mode. This mode shuts down the receive clock when no data is being received to save power. This mode should not be used when PCSBP is enabled and is automatically disabled when the LOOPBK bit in the MR0 register is set.

## Register 23: Ethernet PHY Management Register 17 – Interrupt Control/Status (MR17), address 0x11

This register provides the means for controlling and observing the events which trigger a PHY layer interrupt in the **MACRIS** register. This register can also be used in a polling mode via the Media Independent Interface as a means to observe key events within the PHY layer via one register address. Bits 0 through 7 are status bits which are each set based on an event. These bits are cleared after the register is read. Bits 8 through 15 of this register, when set, enable the corresponding bit in the lower byte to signal a PHY layer interrupt in the **MACRIS** register.

Ethernet PHY Management Register 17 – Interrupt Control/Status (MR17)

Base 0x4004.8000 Address 0x11 Type R/W, reset 0x0000

	15	14	13	12	11	10	9	8	7	6	5	4	3	2	1	0
	JABBER_IE	RXER_IE	PRX_IE	PDF_IE	LPACK_IE	LSCHG_IE	RFAULT_IE	ANEGCOMP_IE	JABBER_INT	RXER_INT	PRX_INT	PDF_INT	LPACK_INT	LSCHG_INT	RFAULT_INT	ANEGCOMP_INT
Type	R/W	R/W	R/W	R/W	R/W	R/W	R/W	R/W	RC	RC	RC	RC	RC	RC	RC	RC
Reset	Λ	Λ	Λ	Λ	Λ	Λ	Λ	0	Λ	Λ	Λ	0	Λ	Λ	0	Λ

eset u	0 0 0	0 0	U		
Bit/Field	Name	Туре	Reset	Description	
15	JABBER_IE	R/W	0	Jabber Interrupt Enable	
				When set, this bit enables system interrupts when a Jabber condition is detected by the Ethernet Controller.	
14	RXER_IE	R/W	0	Receive Error Interrupt Enable	
				When set, this bit enables system interrupts when a receive error is detected by the Ethernet Controller.	
13	PRX_IE	R/W	0	Page Received Interrupt Enable	
				When set, this bit enables system interrupts when a new page is received by the Ethernet Controller.	
12	PDF_IE	R/W	0	Parallel Detection Fault Interrupt Enable	
				When set, this bit enables system interrupts when a Parallel Detection Fault is detected by the Ethernet Controller.	
11	LPACK_IE	R/W	0	LP Acknowledge Interrupt Enable	
				When set, this bit enables system interrupts when FLP bursts are received with the ACK bit in the <b>MR5</b> register during auto-negotiation.	
10	LSCHG_IE	R/W	0	Link Status Change Interrupt Enable	
				When set, this bit enables system interrupts when the link status changes from OK to FAIL. $ \label{eq:particle} % \begin{center} \end{center} % cen$	
9	RFAULT_IE	R/W	0	Remote Fault Interrupt Enable	
				When set, this bit enables system interrupts when a remote fault condition is signaled by the link partner.	
8	ANEGCOMP_IE	R/W	0	Auto-Negotiation Complete Interrupt Enable	
				When set, this bit enables system interrupts when the auto-negotiation sequence has completed successfully.	
7	JABBER_INT	RC	0	Jabber Event Interrupt	
				When set, this bit indicates that a Jabber event has been detected by the 10BASE-T circuitry.	


Bit/Field	Name	Туре	Reset	Description
6	RXER_INT	RC	0	Receive Error Interrupt When set, this bit indicates that a receive error has been detected by the Ethernet Controller.
5	PRX_INT	RC	0	Page Receive Interrupt When set, this bit indicates that a new page has been received from the link partner during auto-negotiation.
4	PDF_INT	RC	0	Parallel Detection Fault Interrupt
				When set, this bit indicates that a parallel detection fault has been detected by the Ethernet Controller during the auto-negotiation process.
3	LPACK_INT	RC	0	LP Acknowledge Interrupt
				When set, this bit indicates that an FLP burst has been received with the ACK bit set in the MR5 register during auto-negotiation.
2	LSCHG_INT	RC	0	Link Status Change Interrupt
				When set, this bit indicates that the link status has changed from OK to $\ensuremath{FAIL}.$
1	RFAULT_INT	RC	0	Remote Fault Interrupt
				When set, this bit indicates that a remote fault condition has been signaled by the link partner.
0	ANEGCOMP_INT	RC	0	Auto-Negotiation Complete Interrupt
				When set, this bit indicates that the auto-negotiation sequence has completed successfully.

## Register 24: Ethernet PHY Management Register 18 – Diagnostic (MR18), address 0x12

This register enables software to diagnose the results of the previous auto-negotiation.

Ethernet PHY Management Register 18 – Diagnostic (MR18)

Base 0x4004.8000 Address 0x12 Type RO, reset 0x0000



eset	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0			
Bi	t/Field		Name		Туре	•	Reset	Desc	ription										
1	5:13		reserved	l	RO		0x0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.											
	12		ANEGF		RC		0	When	n set, this negotiati		ates that			0,	as found oit remain	•			
	11		DPLX		RO		0	Wher denoi	minator	found du	iring the	auto-ne	•	process	ghest con . Otherw nd.				
	10		RATE		RO		0	denoi	minator	found du	ring the	auto-ne		process	ighest co . Otherw d.				
	9		RXSD		RO		0	Wher (in 10	0BASE-	s bit indi	e) or tha	it Manch			n has occ ata has b				
	8	F	RX_LOC	<	RO		0	Wher	,	s bit indi					ocked ont ASE-T or				
	7:0		reserved	l	RO		0x00	comp	atibility v	with futu	re produ	cts, the		reserve	To provided bit sho				

# Register 25: Ethernet PHY Management Register 19 – Transceiver Control (MR19), address 0x13

This register enables software to set the gain of the transmit output to compensate for transformer loss.

Ethernet PHY Management Register 19 – Transceiver Control (MR19)


RO

reserved

0x000

Base 0x4004.8000 Address 0x13 Type R/W, reset 0x4000

13:0



Software should not rely on the value of a reserved bit. To provide

preserved across a read-modify-write operation.


compatibility with future products, the value of a reserved bit should be

# Register 26: Ethernet PHY Management Register 23 – LED Configuration (MR23), address 0x17

This register enables software to select the source that causes the LED1 and LED0 signals to toggle.

Ethernet PHY Management Register 23 – LED Configuration (MR23)

Base 0x4004.8000 Address 0x17 Type R/W, reset 0x0010



Bit/Field	Name	Type	Reset	Description
15:8	reserved	RO	0x00	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
7:4	LED1[3:0]	R/W	0x1	LED1 Source The LED1 field selects the source that toggles the LED1 signal.
				Value Description
				0x0 Link OK
				0x1 RX or TX Activity (Default LED1)
				0x2 Reserved
				0x3 Reserved
				0x4 Reserved
				OVE 100DASE TV mode

0x5 100BASE-TX mode
 0x6 10BASE-T mode
 0x7 Full-Duplex

0x8 Link OK & Blink=RX or TX Activity

3:0 LED0[3:0] R/W 0x0 LED0 Source

The LED0 field selects the source that toggles the LED0 signal.

Value Description

0x0 Link OK (Default LED0)

0x1 RX or TX Activity

0x2 Reserved

0x3 Reserved

0x4 Reserved

0x5 100BASE-TX mode

0x6 10BASE-T mode

0x7 Full-Duplex


0x8 Link OK & Blink=RX or TX Activity

### Register 27: Ethernet PHY Management Register 24 – MDI/MDIX Control (MR24), address 0x18

This register enables software to control the behavior of the MDI/MDIX mux and its switching capabilities.

Ethernet PHY Management Register 24 – MDI/MDIX Control (MR24)

Base 0x4004.8000 Address 0x18 Type R/W, reset 0x00C0



### 14 Analog Comparators

An analog comparator is a peripheral that compares two analog voltages, and provides a logical output that signals the comparison result.

**Note:** Not all comparators have the option to drive an output pin.

The comparator can provide its output to a device pin, acting as a replacement for an analog comparator on the board, or it can be used to signal the application via interrupts or triggers to the ADC to cause it to start capturing a sample sequence. The interrupt generation and ADC triggering logic is separate. This means, for example, that an interrupt can be generated on a rising edge and the ADC triggered on a falling edge.

The Stellaris<sup>®</sup> Analog Comparators module has the following features:

- Two independent integrated analog comparators
- Configurable for output to drive an output pin, generate an interrupt, or initiate an ADC sample sequence
- Compare external pin input to external pin input or to internal programmable voltage reference
- Compare a test voltage against any one of these voltages
  - An individual external reference voltage
  - A shared single external reference voltage
  - A shared internal reference voltage

#### 14.1 Block Diagram

-ve input Comparator +ve input C1+ outpu C1o +ve input (alternate) trigger trigger ACCTL1 ACSTAT1 interrup reference input C0--ve input Comparator 0 +ve input output C0o +ve input (alternate) trigger trigger ACCTL0 ACSTAT0 interrup reference input Voltage Interrupt Control Ref **ACRIS** ACREFCTL internal bus **ACMIS ACINTEN** interrupt

Figure 14-1. Analog Comparator Module Block Diagram

#### 14.2 Signal Description

Table 14-1 on page 522 and Table 14-2 on page 523 list the external signals of the Analog Comparators and describe the function of each. The Analog Comparator output signals are alternate functions for some GPIO signals and default to be GPIO signals at reset. The column in the table below titled "Pin Assignment" lists the possible GPIO pin placements for the Analog Comparator signals. The AFSEL bit in the **GPIO Alternate Function Select (GPIOAFSEL)** register (page 272) should be set to choose the Analog Comparator function. The positive and negative input signals are configured by clearing the DEN bit in the **GPIO Digital Enable (GPIODEN)** register. For more information on configuring GPIOs, see "General-Purpose Input/Outputs (GPIOs)" on page 251.

**Table 14-1. Analog Comparators Signals (100LQFP)** 

Pin Name	Pin Number	Pin Type	Buffer Type <sup>a</sup>	Description
C0+	90	1	Analog	Analog comparator 0 positive input.
C0-	92	I	Analog	Analog comparator 0 negative input.
COo	100	0	TTL	Analog comparator 0 output.
C1+	24	I	Analog	Analog comparator 1 positive input.
C1-	91	I	Analog	Analog comparator 1 negative input.
Clo	24	0	TTL	Analog comparator 1 output.

a. The TTL designation indicates the pin has TTL-compatible voltage levels.

Table 14-2. Analog Comparators Signals (108BGA)

Pin Name	Pin Number	Pin Type	Buffer Type <sup>a</sup>	Description
C0+	A7	I	Analog	Analog comparator 0 positive input.
C0-	A6	I	Analog	Analog comparator 0 negative input.
COo	F1	0	TTL	Analog comparator 0 output.
C1+	M1	I	Analog	Analog comparator 1 positive input.
C1-	B7	I	Analog	Analog comparator 1 negative input.
Clo	M1	0	TTL	Analog comparator 1 output.

a. The TTL designation indicates the pin has TTL-compatible voltage levels.

#### 14.3 Functional Description


**Important:** It is recommended that the Digital-Input enable (the GPIODEN bit in the GPIO module) for the analog input pin be disabled to prevent excessive current draw from the I/O pads.

The comparator compares the VIN- and VIN+ inputs to produce an output, VOUT.

```
VIN- < VIN+, VOUT = 1
VIN- > VIN+, VOUT = 0
```

As shown in Figure 14-2 on page 523, the input source for VIN- is an external input. In addition to an external input, input sources for VIN+ can be the +ve input of comparator 0 or an internal reference.

Figure 14-2. Structure of Comparator Unit



A comparator is configured through two status/control registers (ACCTL and ACSTAT). The internal reference is configured through one control register (ACREFCTL). Interrupt status and control is configured through three registers (ACMIS, ACRIS, and ACINTEN).

Typically, the comparator output is used internally to generate controller interrupts. It may also be used to drive an external pin or generate an analog-to-digital converter (ADC) trigger.

**Important:** The ASRCP bits in the **ACCTLn** register must be set before using the analog comparators.

#### 14.3.1 Internal Reference Programming

The structure of the internal reference is shown in Figure 14-3 on page 524. This is controlled by a single configuration register (**ACREFCTL**). Table 14-3 on page 524 shows the programming options to develop specific internal reference values, to compare an external voltage against a particular voltage generated internally.

Figure 14-3. Comparator Internal Reference Structure




Table 14-3. Internal Reference Voltage and ACREFCTL Field Values

ACREFCTL Regi	ster	Output Beforence Voltage Based on VDEF Field Volus				
EN Bit Value	RNG Bit Value	Output Reference Voltage Based on VREF Field Value				
EN=0	RNG=X	0 V (GND) for any value of VREF; however, it is recommended that RNG=1 and VREF=0 for the least noisy ground reference.				
		Total resistance in ladder is 31 R. $V_{REF} = AV_{DD} \times \frac{Rv_{REF}}{R_T}$ $V_{REF} = AV_{DD} \times \frac{(VREF + 8)}{31}$ $V_{REF} = 0.85 + 0.106 \times VREF$ The range of internal reference in this mode is 0.85-2.448 V.				
EN=1	RNG=1	Total resistance in ladder is 23 R. $V_{\it REF} = AV_{\it DD} \times \frac{Rv_{\it REF}}{R_{\it T}}$ $V_{\it REF} = AV_{\it DD} \times \frac{V_{\it REF}}{23}$ $V_{\it REF} = 0.143 \times V_{\it REF}$ The range of internal reference for this mode is 0-2.152 V.				

### 14.4 Initialization and Configuration

The following example shows how to configure an analog comparator to read back its output value from an internal register.

1. Enable the analog comparator 0 clock by writing a value of 0x0010.0000 to the **RCGC1** register in the System Control module.

- 2. In the GPIO module, enable the GPIO port/pin associated with C0- as a GPIO input.
- 3. Configure the internal voltage reference to 1.65 V by writing the **ACREFCTL** register with the value 0x0000.030C.
- **4.** Configure comparator 0 to use the internal voltage reference and to *not* invert the output by writing the **ACCTL0** register with the value of 0x0000.040C.
- **5.** Delay for some time.
- 6. Read the comparator output value by reading the ACSTAT0 register's OVAL value.

Change the level of the signal input on CO- to see the OVAL value change.

#### 14.5 Register Map

Table 14-4 on page 525 lists the comparator registers. The offset listed is a hexadecimal increment to the register's address, relative to the Analog Comparator base address of 0x4003.C000.

Note that the analog comparator module clock must be enabled before the registers can be programmed (see page 210). There must be a delay of 3 system clocks after the ADC module clock is enabled before any ADC module registers are accessed.

**Table 14-4. Analog Comparators Register Map** 

Offset	Name	Type	Reset	Description	See page
0x000	ACMIS	R/W1C	0x0000.0000	Analog Comparator Masked Interrupt Status	526
0x004	ACRIS	RO	0x0000.0000	Analog Comparator Raw Interrupt Status	527
0x008	ACINTEN	R/W	0x0000.0000	Analog Comparator Interrupt Enable	528
0x010	ACREFCTL	R/W	0x0000.0000	Analog Comparator Reference Voltage Control	529
0x020	ACSTAT0	RO	0x0000.0000	Analog Comparator Status 0	530
0x024	ACCTL0	R/W	0x0000.0000	Analog Comparator Control 0	531
0x040	ACSTAT1	RO	0x0000.0000	Analog Comparator Status 1	530
0x044	ACCTL1	R/W	0x0000.0000	Analog Comparator Control 1	531

### 14.6 Register Descriptions

The remainder of this section lists and describes the Analog Comparator registers, in numerical order by address offset.


### Register 1: Analog Comparator Masked Interrupt Status (ACMIS), offset 0x000

This register provides a summary of the interrupt status (masked) of the comparators.

Analog Comparator Masked Interrupt Status (ACMIS)

Base 0x4003.C000

Offset 0x000 Type R/W1C, reset 0x0000.0000



Bit/Field	Name	Type	Reset	Description
31:2	reserved	RO	0x00	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
1	IN1	R/W1C	0	Comparator 1 Masked Interrupt Status
				Gives the masked interrupt state of this interrupt. Write 1 to this bit to clear the pending interrupt.
0	IN0	R/W1C	0	Comparator 0 Masked Interrupt Status
				Gives the masked interrupt state of this interrupt. Write 1 to this bit to clear the pending interrupt.


#### Register 2: Analog Comparator Raw Interrupt Status (ACRIS), offset 0x004

This register provides a summary of the interrupt status (raw) of the comparators.

Analog Comparator Raw Interrupt Status (ACRIS)

Base 0x4003.C000 Offset 0x004

Type RO, reset 0x0000.0000



Bit/Field	Name	Type	Reset	Description
31:2	reserved	RO	0x00	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
1	IN1	RO	0	Comparator 1 Interrupt Status  When set, indicates that an interrupt has been generated by comparator  1.
0	IN0	RO	0	Comparator 0 Interrupt Status  When set, indicates that an interrupt has been generated by comparator 0.


#### Register 3: Analog Comparator Interrupt Enable (ACINTEN), offset 0x008

This register provides the interrupt enable for the comparators.

Analog Comparator Interrupt Enable (ACINTEN)

Base 0x4003.C000

Offset 0x008 Type R/W, reset 0x0000.0000



Bit/Field	Name	Type	Reset	Description
31:2	reserved	RO	0x00	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
1	IN1	R/W	0	Comparator 1 Interrupt Enable When set, enables the controller interrupt from the comparator 1 output.
0	IN0	R/W	0	Comparator 0 Interrupt Enable  When set, enables the controller interrupt from the comparator 0 output.


#### Register 4: Analog Comparator Reference Voltage Control (ACREFCTL), offset 0x010

This register specifies whether the resistor ladder is powered on as well as the range and tap.

Analog Comparator Reference Voltage Control (ACREFCTL)

Base 0x4003.C000

Offset 0x010 Type R/W, reset 0x0000.0000



Bit/Field	Name	Туре	Reset	Description
31:10	reserved	RO	0x00	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
9	EN	R/W	0	Resistor Ladder Enable
				The EN bit specifies whether the resistor ladder is powered on. If 0, the resistor ladder is unpowered. If 1, the resistor ladder is connected to the analog $V_{\rm DD}$ .
				This bit is reset to 0 so that the internal reference consumes the least amount of power if not used and programmed.
8	RNG	R/W	0	Resistor Ladder Range
				The RNG bit specifies the range of the resistor ladder. If 0, the resistor ladder has a total resistance of 31 R. If 1, the resistor ladder has a total resistance of 23 R.
7:4	reserved	RO	0x00	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
3:0	VREF	R/W	0x00	Resistor Ladder Voltage Ref


The VREF bit field specifies the resistor ladder tap that is passed through an analog multiplexer. The voltage corresponding to the tap position is the internal reference voltage available for comparison. See Table 14-3 on page 524 for some output reference voltage examples.

### Register 5: Analog Comparator Status 0 (ACSTAT0), offset 0x020 Register 6: Analog Comparator Status 1 (ACSTAT1), offset 0x040

These registers specify the current output value of the comparator.

#### Analog Comparator Status 0 (ACSTAT0)

Base 0x4003.C000 Offset 0x020 Type RO, reset 0x0000.0000



Bit/Field	Name	Type	Reset	Description
31:2	reserved	RO	0x00	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
1	OVAL	RO	0	Comparator Output Value  The OVAL bit specifies the current output value of the comparator.
0	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.

### Register 7: Analog Comparator Control 0 (ACCTL0), offset 0x024 Register 8: Analog Comparator Control 1 (ACCTL1), offset 0x044


These registers configure the comparator's input and output.

Analog Comparator Control 0 (ACCTL0)

Name

Base 0x4003.C000 Offset 0x024 Type R/W, reset 0x0000.0000

Bit/Field



Description

Reset

Type

		• •		·
31:12	reserved	RO	0x00	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
11	TOEN	R/W	0	Trigger Output Enable
				The TOEN bit enables the ADC event transmission to the ADC. If 0, the event is suppressed and not sent to the ADC. If 1, the event is transmitted to the ADC.
10:9	ASRCP	R/W	0x00	Analog Source Positive
				The ASRCP field specifies the source of input voltage to the VIN+ terminal of the comparator. The encodings for this field are as follows:
				Value Function
				0x0 Pin value
				0x1 Pin value of C0+
				0x2 Internal voltage reference
				0x3 Reserved
8	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
7	TSLVAL	R/W	0	Trigger Sense Level Value

The TSLVAL bit specifies the sense value of the input that generates an ADC event if in Level Sense mode. If 0, an ADC event is generated if the comparator output is Low. Otherwise, an ADC event is generated

if the comparator output is High.

November 18, 2011 531

Bit/Field	Name	Туре	Reset	Description
6:5	TSEN	R/W	0x0	Trigger Sense The TSEN field specifies the sense of the comparator output that generates an ADC event. The sense conditioning is as follows:
				Value Function
				0x0 Level sense, see TSLVAL
				0x1 Falling edge
				0x2 Rising edge
				0x3 Either edge
4	ISLVAL	R/W	0	Interrupt Sense Level Value
				The ISLVAL bit specifies the sense value of the input that generates an interrupt if in Level Sense mode. If 0, an interrupt is generated if the comparator output is Low. Otherwise, an interrupt is generated if the comparator output is High.
3:2	ISEN	R/W	0x0	Interrupt Sense
				The ISEN field specifies the sense of the comparator output that generates an interrupt. The sense conditioning is as follows:
				Value Function
				0x0 Level sense, see ISLVAL
				0x1 Falling edge
				0x2 Rising edge
				0x3 Either edge
1	CINV	R/W	0	Comparator Output Invert
				The CINV bit conditionally inverts the output of the comparator. If 0, the output of the comparator is unchanged. If 1, the output of the comparator is inverted prior to being processed by hardware.
0	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.

### 15 Pin Diagram

The LM3S6422 microcontroller pin diagrams are shown below.

Figure 15-1. 100-Pin LQFP Package Pin Diagram




Figure 15-2. 108-Ball BGA Package Pin Diagram (Top View)

	1	2	3	4	5	6	7	8	9	10	11	12	
Α	ADC1	NC	(NC)	NC	GNDA	PB4 C0-	PB6 C0+	PB7 TRST	PC0 TCK SWCLK	PC3 TDO SWO	NC	NC	Α
В	ADC0	NC NC	NC NC	NC	GNDA	GND	PB5 C1-	PC2 TDI	PC1 TMS SWDIO	CMOD1	NC	NC	В
С	NC (	NC	VDD25	GND	GND	VDDA	VDDA	GNDPHY	GNDPHY	VCCPHY	PB2	PB3	С
D	NC (	NC	VDD25							VCCPHY	VCCPHY	PB1 CCP2	D
E	PD4	PD5	LDO							VDD33	CMOD0	PB0 CCP0	Ε
F	PD7 C0o	PD6	VDD25							GND	GND	GND	F
G	PDO	PD1	VDD25			LM3	S6422			VDD33	VDD33	VDD33	G
Н	PD3	PD2	GND							VDD33	RST	PF1	Н
J	XTALNPHY	KTALPPHY	GND		_					GND	PF2 LED1	PF3 LED0	J
K	NC	NC	ERBIAS	GNDPHY	GND	GND	VDD33	VDD33	VDD33	GND	NC	NC	K
L	PC4	NC	PA0 U0Rx	PA3 SSI0Fss	PA4 SSIORX	PA6 CCP1	RXIN	TXON	MDIO	GND	OSC0	VDD	L
М	PC5 C1+ C10	PC6 CCP3	PA1 UOTx	PA2 SSIOC1k	PA5 SSIOTX	NC	RXIP	TXOP	PF0	NC	OSC1	NC	M
	1	2	3	4	5	6	7	8	9	10	11	12	

### 16 Signal Tables

The following tables list the signals available for each pin. Functionality is enabled by software with the **GPIOAFSEL** register.

**Important:** All multiplexed pins are GPIOs by default, with the exception of the five JTAG pins (PB7 and PC[3:0]) which default to the JTAG functionality.

Table 16-1 on page 535 shows the pin-to-signal-name mapping, including functional characteristics of the signals. Table 16-2 on page 539 lists the signals in alphabetical order by signal name.

Table 16-3 on page 542 groups the signals by functionality, except for GPIOs. Table 16-4 on page 545 lists the GPIO pins and their alternate functionality.

Note: All digital inputs are Schmitt triggered.

### 16.1 100-Pin LQFP Package Pin Tables

Table 16-1. Signals by Pin Number

Pin Number	Pin Name	Pin Type	Buffer Type <sup>a</sup>	Description
1	ADC0	I	Analog	Analog-to-digital converter input 0.
2	ADC1	I	Analog	Analog-to-digital converter input 1.
3	VDDA	-	Power	The positive supply (3.3 V) for the analog circuits (ADC, Analog Comparators, etc.). These are separated from VDD to minimize the electrical noise contained on VDD from affecting the analog functions. VDDA pins must be connected to 3.3 V, regardless of system implementation.
4	GNDA	-	Power	The ground reference for the analog circuits (ADC, Analog Comparators, etc.). These are separated from GND to minimize the electrical noise contained on VDD from affecting the analog functions.
5	NC	-	-	No connect. Leave the pin electrically unconnected/isolated.
6	NC	-	-	No connect. Leave the pin electrically unconnected/isolated.
7	LDO	-	Power	Low drop-out regulator output voltage. This pin requires an external capacitor between the pin and GND of 1 $\mu\text{F}$ or greater. When the on-chip LDO is used to provide power to the logic, the LDO pin must also be connected to the VDD25 pins at the board level in addition to the decoupling capacitor(s).
8	VDD	-	Power	Positive supply for I/O and some logic.
9	GND	-	Power	Ground reference for logic and I/O pins.
10	PD0	I/O	TTL	GPIO port D bit 0.
11	PD1	I/O	TTL	GPIO port D bit 1.
12	PD2	I/O	TTL	GPIO port D bit 2.
13	PD3	I/O	TTL	GPIO port D bit 3.
14	VDD25	-	Power	Positive supply for most of the logic function, including the processor core and most peripherals.
15	GND	-	Power	Ground reference for logic and I/O pins.
16	XTALPPHY	I	TTL	Ethernet PHY XTALP 25-MHz oscillator crystal input or external clock reference input.

Table 16-1. Signals by Pin Number (continued)

Pin Number	Pin Name	Pin Type	Buffer Type <sup>a</sup>	Description
17	XTALNPHY	0	TTL	Ethernet PHY XTALN 25-MHz oscillator crystal output. Leave unconnected when using a single-ended 25-MHz clock input connected to the XTALPPHY pin.
18	NC	-	-	No connect. Leave the pin electrically unconnected/isolated.
19	NC	-	-	No connect. Leave the pin electrically unconnected/isolated.
20	VDD	-	Power	Positive supply for I/O and some logic.
21	GND	-	Power	Ground reference for logic and I/O pins.
22	NC	-	-	No connect. Leave the pin electrically unconnected/isolated.
22	PC6	I/O	TTL	GPIO port C bit 6.
23	CCP3	I/O	TTL	Capture/Compare/PWM 3.
	PC5	I/O	TTL	GPIO port C bit 5.
24	C1+	I	Analog	Analog comparator 1 positive input.
	Clo	0	TTL	Analog comparator 1 output.
25	PC4	I/O	TTL	GPIO port C bit 4.
	PA0	I/O	TTL	GPIO port A bit 0.
26	U0Rx	I	TTL	UART module 0 receive. When in IrDA mode, this signal has IrDA modulation.
	PA1	I/O	TTL	GPIO port A bit 1.
27	UOTx	0	TTL	UART module 0 transmit. When in IrDA mode, this signal has IrDA modulation.
00	PA2	I/O	TTL	GPIO port A bit 2.
28	SSI0Clk	I/O	TTL	SSI module 0 clock.
20	PA3	I/O	TTL	GPIO port A bit 3.
29	SSI0Fss	I/O	TTL	SSI module 0 frame.
20	PA4	I/O	TTL	GPIO port A bit 4.
30	SSI0Rx	I	TTL	SSI module 0 receive.
24	PA5	I/O	TTL	GPIO port A bit 5.
31	SSIOTx	0	TTL	SSI module 0 transmit.
32	VDD	-	Power	Positive supply for I/O and some logic.
33	GND	-	Power	Ground reference for logic and I/O pins.
24	PA6	I/O	TTL	GPIO port A bit 6.
34	CCP1	I/O	TTL	Capture/Compare/PWM 1.
35	NC	-	-	No connect. Leave the pin electrically unconnected/isolated.
36	VCCPHY	-	Power	VCC of the Ethernet PHY.
37	RXIN	I	Analog	RXIN of the Ethernet PHY.
38	VDD25	-	Power	Positive supply for most of the logic function, including the processor core and most peripherals.
39	GND	-	Power	Ground reference for logic and I/O pins.
40	RXIP	ı	Analog	RXIP of the Ethernet PHY.
41	ERBIAS	ı	Analog	12.4-kΩ resistor (1% precision) used internally for Ethernet PHY.
42	GNDPHY	-	Power	GND of the Ethernet PHY.
43	TXOP	0	Analog	TXOP of the Ethernet PHY.
44	VDD	-	Power	Positive supply for I/O and some logic.

Table 16-1. Signals by Pin Number (continued)

Pin Number	Pin Name	Pin Type	Buffer Type <sup>a</sup>	Description
45	GND	-	Power	Ground reference for logic and I/O pins.
46	TXON	0	Analog	TXON of the Ethernet PHY.
47	PF0	I/O	TTL	GPIO port F bit 0.
48	OSC0	I I	Analog	Main oscillator crystal input or an external clock reference input.
49	OSC1	0	Analog	Main oscillator crystal output. Leave unconnected when using a single-ended clock source.
50	NC	-	-	No connect. Leave the pin electrically unconnected/isolated.
51	NC	-	-	No connect. Leave the pin electrically unconnected/isolated.
52	NC	-	-	No connect. Leave the pin electrically unconnected/isolated.
53	NC	-	-	No connect. Leave the pin electrically unconnected/isolated.
54	GND	-	Power	Ground reference for logic and I/O pins.
55	VDD	-	Power	Positive supply for I/O and some logic.
56	VDD	-	Power	Positive supply for I/O and some logic.
57	GND	-	Power	Ground reference for logic and I/O pins.
58	MDIO	I/O	TTL	MDIO of the Ethernet PHY.
50	PF3	I/O	TTL	GPIO port F bit 3.
59 –	LED0	0	TTL	Ethernet LED 0.
00	PF2	I/O	TTL	GPIO port F bit 2.
60 –	LED1	0	TTL	Ethernet LED 1.
61	PF1	I/O	TTL	GPIO port F bit 1.
62	VDD25	-	Power	Positive supply for most of the logic function, including the processor core and most peripherals.
63	GND	-	Power	Ground reference for logic and I/O pins.
64	RST	l l	TTL	System reset input.
65	CMOD0	1	TTL	CPU Mode bit 0. Input must be set to logic 0 (grounded); other encodings reserved.
66	PB0	I/O	TTL	GPIO port B bit 0.
66	CCP0	I/O	TTL	Capture/Compare/PWM 0.
67	PB1	I/O	TTL	GPIO port B bit 1.
67 –	CCP2	I/O	TTL	Capture/Compare/PWM 2.
68	VDD	-	Power	Positive supply for I/O and some logic.
69	GND	-	Power	Ground reference for logic and I/O pins.
70	PB2	I/O	TTL	GPIO port B bit 2.
71	PB3	I/O	TTL	GPIO port B bit 3.
72	NC	-	-	No connect. Leave the pin electrically unconnected/isolated.
73	NC	-	-	No connect. Leave the pin electrically unconnected/isolated.
74	NC	-	-	No connect. Leave the pin electrically unconnected/isolated.
75	NC	-	-	No connect. Leave the pin electrically unconnected/isolated.
76	CMOD1	1	TTL	CPU Mode bit 1. Input must be set to logic 0 (grounded); other encodings reserved.
	PC3	I/O	TTL	GPIO port C bit 3.
77	SWO	0	TTL	JTAG TDO and SWO.
	TDO	0	TTL	JTAG TDO and SWO.

Table 16-1. Signals by Pin Number (continued)

Pin Number	Pin Name	Pin Type	Buffer Type <sup>a</sup>	Description
78	PC2	I/O	TTL	GPIO port C bit 2.
/*	TDI	I	TTL	JTAG TDI.
	PC1	I/O	TTL	GPIO port C bit 1.
79	SWDIO	I/O	TTL	JTAG TMS and SWDIO.
	TMS	I/O	TTL	JTAG TMS and SWDIO.
	PC0	I/O	TTL	GPIO port C bit 0.
80	SWCLK	I	TTL	JTAG/SWD CLK.
	TCK	I	TTL	JTAG/SWD CLK.
81	VDD	-	Power	Positive supply for I/O and some logic.
82	GND	-	Power	Ground reference for logic and I/O pins.
83	VCCPHY	-	Power	VCC of the Ethernet PHY.
84	VCCPHY	-	Power	VCC of the Ethernet PHY.
85	GNDPHY	-	Power	GND of the Ethernet PHY.
86	GNDPHY	-	Power	GND of the Ethernet PHY.
87	GND	-	Power	Ground reference for logic and I/O pins.
88	VDD25	-	Power	Positive supply for most of the logic function, including the processor core and most peripherals.
89	PB7	I/O	TTL	GPIO port B bit 7.
09	TRST	I	TTL	JTAG TRST.
90	PB6	I/O	TTL	GPIO port B bit 6.
90	C0+	I	Analog	Analog comparator 0 positive input.
91	PB5	I/O	TTL	GPIO port B bit 5.
91	C1-	I	Analog	Analog comparator 1 negative input.
92	PB4	I/O	TTL	GPIO port B bit 4.
92	C0-	I	Analog	Analog comparator 0 negative input.
93	VDD	-	Power	Positive supply for I/O and some logic.
94	GND	-	Power	Ground reference for logic and I/O pins.
95	PD4	I/O	TTL	GPIO port D bit 4.
96	PD5	I/O	TTL	GPIO port D bit 5.
97	GNDA	-	Power	The ground reference for the analog circuits (ADC, Analog Comparators, etc.). These are separated from GND to minimize the electrical noise contained on VDD from affecting the analog functions.
98	VDDA	-	Power	The positive supply (3.3 V) for the analog circuits (ADC, Analog Comparators, etc.). These are separated from VDD to minimize the electrical noise contained on VDD from affecting the analog functions. VDDA pins must be connected to 3.3 V, regardless of system implementation.
99	PD6	I/O	TTL	GPIO port D bit 6.
100	PD7	I/O	TTL	GPIO port D bit 7.
100	C0o	0	TTL	Analog comparator 0 output.

a. The TTL designation indicates the pin has TTL-compatible voltage levels.

Table 16-2. Signals by Signal Name

Pin Name	Pin Number	Pin Type	Buffer Type <sup>a</sup>	Description
ADC0	1	I	Analog	Analog-to-digital converter input 0.
ADC1	2	I	Analog	Analog-to-digital converter input 1.
C0+	90	ļ	Analog	Analog comparator 0 positive input.
C0-	92	I	Analog	Analog comparator 0 negative input.
C0o	100	0	TTL	Analog comparator 0 output.
C1+	24	I	Analog	Analog comparator 1 positive input.
C1-	91	I	Analog	Analog comparator 1 negative input.
Clo	24	0	TTL	Analog comparator 1 output.
CCP0	66	I/O	TTL	Capture/Compare/PWM 0.
CCP1	34	I/O	TTL	Capture/Compare/PWM 1.
CCP2	67	I/O	TTL	Capture/Compare/PWM 2.
CCP3	23	I/O	TTL	Capture/Compare/PWM 3.
CMOD0	65	I	TTL	CPU Mode bit 0. Input must be set to logic 0 (grounded); other encodings reserved.
CMOD1	76	I	TTL	CPU Mode bit 1. Input must be set to logic 0 (grounded); other encodings reserved.
ERBIAS	41	I	Analog	12.4-k $\Omega$ resistor (1% precision) used internally for Ethernet PHY.
GND	9 15 21 33 39 45 54 57 63 69 82 87 94	-	Power	Ground reference for logic and I/O pins.
GNDA	4 97	-	Power	The ground reference for the analog circuits (ADC, Analog Comparators, etc.). These are separated from GND to minimize the electrical noise contained on VDD from affecting the analog functions.
GNDPHY	42 85 86	-	Power	GND of the Ethernet PHY.
LDO	7	-	Power	Low drop-out regulator output voltage. This pin requires an external capacitor between the pin and GND of 1 $\mu$ F or greater. When the on-chip LDO is used to provide power to the logic, the LDO pin must also be connected to the VDD25 pins at the board level in addition to the decoupling capacitor(s).
LED0	59	0	TTL	Ethernet LED 0.
LED1	60	0	TTL	Ethernet LED 1.
MDIO	58	I/O	TTL	MDIO of the Ethernet PHY.

Table 16-2. Signals by Signal Name (continued)

Pin Name	Pin Number	Pin Type	Buffer Type <sup>a</sup>	Description
NC	5	-	-	No connect. Leave the pin electrically unconnected/isolated.
	6 18			
	19			
	22			
	35 50			
	51			
	52			
	53 72			
	73			
	74			
	75			
osc0	48	I	Analog	Main oscillator crystal input or an external clock reference input.
osc1	49	0	Analog	Main oscillator crystal output. Leave unconnected when using a single-ended clock source.
PA0	26	I/O	TTL	GPIO port A bit 0.
PA1	27	I/O	TTL	GPIO port A bit 1.
PA2	28	I/O	TTL	GPIO port A bit 2.
PA3	29	I/O	TTL	GPIO port A bit 3.
PA4	30	I/O	TTL	GPIO port A bit 4.
PA5	31	I/O	TTL	GPIO port A bit 5.
PA6	34	I/O	TTL	GPIO port A bit 6.
PB0	66	I/O	TTL	GPIO port B bit 0.
PB1	67	I/O	TTL	GPIO port B bit 1.
PB2	70	I/O	TTL	GPIO port B bit 2.
PB3	71	I/O	TTL	GPIO port B bit 3.
PB4	92	I/O	TTL	GPIO port B bit 4.
PB5	91	I/O	TTL	GPIO port B bit 5.
PB6	90	I/O	TTL	GPIO port B bit 6.
PB7	89	I/O	TTL	GPIO port B bit 7.
PC0	80	I/O	TTL	GPIO port C bit 0.
PC1	79	I/O	TTL	GPIO port C bit 1.
PC2	78	I/O	TTL	GPIO port C bit 2.
PC3	77	I/O	TTL	GPIO port C bit 3.
PC4	25	I/O	TTL	GPIO port C bit 4.
PC5	24	I/O	TTL	GPIO port C bit 5.
PC6	23	I/O	TTL	GPIO port C bit 6.
PD0	10	I/O	TTL	GPIO port D bit 0.
PD1	11	I/O	TTL	GPIO port D bit 1.
PD2	12	I/O	TTL	GPIO port D bit 2.
PD3	13	I/O	TTL	GPIO port D bit 3.
PD4	95	I/O	TTL	GPIO port D bit 4.
PD5	96	I/O	TTL	GPIO port D bit 5.

Table 16-2. Signals by Signal Name (continued)

Pin Name	Pin Number	Pin Type	Buffer Type <sup>a</sup>	Description
PD6	99	I/O	TTL	GPIO port D bit 6.
PD7	100	I/O	TTL	GPIO port D bit 7.
PF0	47	I/O	TTL	GPIO port F bit 0.
PF1	61	I/O	TTL	GPIO port F bit 1.
PF2	60	I/O	TTL	GPIO port F bit 2.
PF3	59	I/O	TTL	GPIO port F bit 3.
RST	64	ļ	TTL	System reset input.
RXIN	37	I	Analog	RXIN of the Ethernet PHY.
RXIP	40	I	Analog	RXIP of the Ethernet PHY.
SSIOClk	28	I/O	TTL	SSI module 0 clock.
SSI0Fss	29	I/O	TTL	SSI module 0 frame.
SSI0Rx	30	I	TTL	SSI module 0 receive.
SSIOTx	31	0	TTL	SSI module 0 transmit.
SWCLK	80	I	TTL	JTAG/SWD CLK.
SWDIO	79	I/O	TTL	JTAG TMS and SWDIO.
SWO	77	0	TTL	JTAG TDO and SWO.
TCK	80	I	TTL	JTAG/SWD CLK.
TDI	78	1	TTL	JTAG TDI.
TDO	77	0	TTL	JTAG TDO and SWO.
TMS	79	I/O	TTL	JTAG TMS and SWDIO.
TRST	89	I	TTL	JTAG TRST.
TXON	46	0	Analog	TXON of the Ethernet PHY.
TXOP	43	0	Analog	TXOP of the Ethernet PHY.
UORx	26	1	TTL	UART module 0 receive. When in IrDA mode, this signal has IrDA modulation.
UOTx	27	0	TTL	UART module 0 transmit. When in IrDA mode, this signal has IrDA modulation.
VCCPHY	36 83 84	-	Power	VCC of the Ethernet PHY.
VDD	8 20 32 44 55 56 68 81 93	-	Power	Positive supply for I/O and some logic.
VDD25	14 38 62 88	-	Power	Positive supply for most of the logic function, including the processor core and most peripherals.

Table 16-2. Signals by Signal Name (continued)

Pin Name	Pin Number	Pin Type	Buffer Type <sup>a</sup>	Description
VDDA	3 98	-	Power	The positive supply (3.3 V) for the analog circuits (ADC, Analog Comparators, etc.). These are separated from VDD to minimize the electrical noise contained on VDD from affecting the analog functions. VDDA pins must be connected to 3.3 V, regardless of system implementation.
XTALNPHY	17	0	TTL	Ethernet PHY XTALN 25-MHz oscillator crystal output. Leave unconnected when using a single-ended 25-MHz clock input connected to the XTALPPHY pin.
XTALPPHY	16	I	TTL	Ethernet PHY XTALP 25-MHz oscillator crystal input or external clock reference input.

a. The TTL designation indicates the pin has TTL-compatible voltage levels.

Table 16-3. Signals by Function, Except for GPIO

Function	Pin Name	Pin Number	Pin Type	Buffer Type <sup>a</sup>	Description
ADC	ADC0	1	I	Analog	Analog-to-digital converter input 0.
ADC	ADC1	2	Ι	Analog	Analog-to-digital converter input 1.
	C0+	90	I	Analog	Analog comparator 0 positive input.
	C0-	92	I	Analog	Analog comparator 0 negative input.
Analog Comparators	C0o	100	0	TTL	Analog comparator 0 output.
Analog Comparators	C1+	24	I	Analog	Analog comparator 1 positive input.
	C1-	91	I	Analog	Analog comparator 1 negative input.
	Clo	24	0	TTL	Analog comparator 1 output.
	ERBIAS	41	I	Analog	12.4-k $\Omega$ resistor (1% precision) used internally for Ethernet PHY.
	GNDPHY	42 85 86	-	Power	GND of the Ethernet PHY.
	LED0	59	0	TTL	Ethernet LED 0.
	LED1	60	0	TTL	Ethernet LED 1.
	MDIO	58	I/O	TTL	MDIO of the Ethernet PHY.
	RXIN	37	I	Analog	RXIN of the Ethernet PHY.
Ethernet	RXIP	40	I	Analog	RXIP of the Ethernet PHY.
Ethernet	TXON	46	0	Analog	TXON of the Ethernet PHY.
	TXOP	43	0	Analog	TXOP of the Ethernet PHY.
	VCCPHY	36 83 84	-	Power	VCC of the Ethernet PHY.
	XTALNPHY	17	0	TTL	Ethernet PHY XTALN 25-MHz oscillator crystal output. Leave unconnected when using a single-ended 25-MHz clock input connected to the XTALPPHY pin.
	XTALPPHY	16	I	TTL	Ethernet PHY XTALP 25-MHz oscillator crystal input or external clock reference input.

Table 16-3. Signals by Function, Except for GPIO (continued)

Function	Pin Name	Pin Number	Pin Type	Buffer Type <sup>a</sup>	Description
	CCP0	66	I/O	TTL	Capture/Compare/PWM 0.
General-Purpose	CCP1	34	I/O	TTL	Capture/Compare/PWM 1.
Timers	CCP2	67	I/O	TTL	Capture/Compare/PWM 2.
	CCP3	23	I/O	TTL	Capture/Compare/PWM 3.
	SWCLK	80	I	TTL	JTAG/SWD CLK.
	SWDIO	79	I/O	TTL	JTAG TMS and SWDIO.
	SWO	77	0	TTL	JTAG TDO and SWO.
JTAG/SWD/SWO	TCK	80	I	TTL	JTAG/SWD CLK.
31AG/3WD/3WO	TDI	78	I	TTL	JTAG TDI.
	TDO	77	0	TTL	JTAG TDO and SWO.
	TMS	79	I/O	TTL	JTAG TMS and SWDIO.
	TRST	89	I	TTL	JTAG TRST.

Table 16-3. Signals by Function, Except for GPIO (continued)

Function	Pin Name	Pin Number	Pin Type	Buffer Type <sup>a</sup>	Description
	GND	9 15 21 33 39 45 54 57 63 69 82 87	-	Power	Ground reference for logic and I/O pins.
	GNDA	4 97	-	Power	The ground reference for the analog circuits (ADC, Analog Comparators, etc.). These are separated from GND to minimize the electrical noise contained on VDD from affecting the analog functions.
Power	LDO	7	-	Power	Low drop-out regulator output voltage. This pin requires an external capacitor between the pin and GND of 1 $\mu$ F or greater. When the on-chip LDO is used to provide power to the logic, the LDO pin must also be connected to the VDD25 pins at the board level in addition to the decoupling capacitor(s).
	VDD	8 20 32 44 55 56 68 81 93	-	Power	Positive supply for I/O and some logic.
	VDD25	14 38 62 88	-	Power	Positive supply for most of the logic function, including the processor core and most peripherals.
	VDDA	3 98	-	Power	The positive supply (3.3 V) for the analog circuits (ADC, Analog Comparators, etc.). These are separated from VDD to minimize the electrical noise contained on VDD from affecting the analog functions. VDDA pins must be connected to 3.3 V, regardless of system implementation.
	SSI0Clk	28	I/O	TTL	SSI module 0 clock.
eei	SSI0Fss	29	I/O	TTL	SSI module 0 frame.
SSI	SSI0Rx	30	I	TTL	SSI module 0 receive.
	SSIOTx	31	0	TTL	SSI module 0 transmit.

Table 16-3. Signals by Function, Except for GPIO (continued)

Function	Pin Name	Pin Number	Pin Type	Buffer Type <sup>a</sup>	Description
	CMOD0	65	I	TTL	CPU Mode bit 0. Input must be set to logic 0 (grounded); other encodings reserved.
	CMOD1	76	I	TTL	CPU Mode bit 1. Input must be set to logic 0 (grounded); other encodings reserved.
System Control & Clocks	osc0	48	I	Analog	Main oscillator crystal input or an external clock reference input.
	osc1	49	0	Analog	Main oscillator crystal output. Leave unconnected when using a single-ended clock source.
	RST	64	I	TTL	System reset input.
UART	U0Rx	26	I	TTL	UART module 0 receive. When in IrDA mode, this signal has IrDA modulation.
OAICI	UOTx	27	0	TTL	UART module 0 transmit. When in IrDA mode, this signal has IrDA modulation.

a. The TTL designation indicates the pin has TTL-compatible voltage levels.

Table 16-4. GPIO Pins and Alternate Functions

10	Pin Number	Multiplexed Function	Multiplexed Function
PA0	26	U0Rx	
PA1	27	UOTx	
PA2	28	SSI0Clk	
PA3	29	SSI0Fss	
PA4	30	SSI0Rx	
PA5	31	SSIOTx	
PA6	34	CCP1	
PB0	66	CCP0	
PB1	67	CCP2	
PB2	70		
PB3	71		
PB4	92	C0-	
PB5	91	C1-	
PB6	90	C0+	
PB7	89	TRST	
PC0	80	TCK	SWCLK
PC1	79	TMS	SWDIO
PC2	78	TDI	
PC3	77	TDO	SWO
PC4	25		
PC5	24	C1+	Clo
PC6	23	CCP3	
PD0	10		
PD1	11		
PD2	12		
PD3	13		

Table 16-4. GPIO Pins and Alternate Functions (continued)

10	Pin Number	Multiplexed Function	Multiplexed Function
PD4	95		
PD5	96		
PD6	99		
PD7	100	COo	
PF0	47		
PF1	61		
PF2	60	LED1	
PF3	59	LED0	

# 16.2 108-Ball BGA Package Pin Tables

Table 16-5. Signals by Pin Number

Pin Number	Pin Name	Pin Type	Buffer Type <sup>a</sup>	Description
A1	ADC1	I	Analog	Analog-to-digital converter input 1.
A2	NC	-	-	No connect. Leave the pin electrically unconnected/isolated.
A3	NC	-	-	No connect. Leave the pin electrically unconnected/isolated.
A4	NC	-	-	No connect. Leave the pin electrically unconnected/isolated.
A5	GNDA	-	Power	The ground reference for the analog circuits (ADC, Analog Comparators, etc.). These are separated from GND to minimize the electrical noise contained on VDD from affecting the analog functions.
A6	PB4	I/O	TTL	GPIO port B bit 4.
Au	C0-	I	Analog	Analog comparator 0 negative input.
A7	PB6	I/O	TTL	GPIO port B bit 6.
A	C0+	I	Analog	Analog comparator 0 positive input.
A8	PB7	I/O	TTL	GPIO port B bit 7.
Ao	TRST	I	TTL	JTAG TRST.
	PC0	I/O	TTL	GPIO port C bit 0.
A9	SWCLK	I	TTL	JTAG/SWD CLK.
	TCK	I	TTL	JTAG/SWD CLK.
	PC3	I/O	TTL	GPIO port C bit 3.
A10	SWO	0	TTL	JTAG TDO and SWO.
	TDO	0	TTL	JTAG TDO and SWO.
A11	NC	-	-	No connect. Leave the pin electrically unconnected/isolated.
A12	NC	-	-	No connect. Leave the pin electrically unconnected/isolated.
B1	ADC0	I	Analog	Analog-to-digital converter input 0.
B2	NC	-	-	No connect. Leave the pin electrically unconnected/isolated.
В3	NC	-	-	No connect. Leave the pin electrically unconnected/isolated.
B4	NC	-	-	No connect. Leave the pin electrically unconnected/isolated.
B5	GNDA	-	Power	The ground reference for the analog circuits (ADC, Analog Comparators, etc.). These are separated from GND to minimize the electrical noise contained on VDD from affecting the analog functions.

Table 16-5. Signals by Pin Number (continued)

Pin Number	Pin Name	Pin Type	Buffer Type <sup>a</sup>	Description
B6	GND	-	Power	Ground reference for logic and I/O pins.
D.7	PB5	I/O	TTL	GPIO port B bit 5.
B7 —	C1-	I	Analog	Analog comparator 1 negative input.
DO	PC2	I/O	TTL	GPIO port C bit 2.
B8 —	TDI	I	TTL	JTAG TDI.
	PC1	I/O	TTL	GPIO port C bit 1.
В9	SWDIO	I/O	TTL	JTAG TMS and SWDIO.
	TMS	I/O	TTL	JTAG TMS and SWDIO.
B10	CMOD1	I	TTL	CPU Mode bit 1. Input must be set to logic 0 (grounded); other encodings reserved.
B11	NC	-	-	No connect. Leave the pin electrically unconnected/isolated.
B12	NC	-	-	No connect. Leave the pin electrically unconnected/isolated.
C1	NC	-	-	No connect. Leave the pin electrically unconnected/isolated.
C2	NC	-	-	No connect. Leave the pin electrically unconnected/isolated.
C3	VDD25	-	Power	Positive supply for most of the logic function, including the processor core and most peripherals.
C4	GND	-	Power	Ground reference for logic and I/O pins.
C5	GND	-	Power	Ground reference for logic and I/O pins.
C6	VDDA	-	Power	The positive supply (3.3 V) for the analog circuits (ADC, Analog Comparators, etc.). These are separated from VDD to minimize the electrical noise contained on VDD from affecting the analog functions. VDDA pins must be connected to 3.3 V, regardless of system implementation.
C7	VDDA	-	Power	The positive supply (3.3 V) for the analog circuits (ADC, Analog Comparators, etc.). These are separated from VDD to minimize the electrical noise contained on VDD from affecting the analog functions. VDDA pins must be connected to 3.3 V, regardless of system implementation.
C8	GNDPHY	-	Power	GND of the Ethernet PHY.
C9	GNDPHY	-	Power	GND of the Ethernet PHY.
C10	VCCPHY	-	Power	VCC of the Ethernet PHY.
C11	PB2	I/O	TTL	GPIO port B bit 2.
C12	PB3	I/O	TTL	GPIO port B bit 3.
D1	NC	-	-	No connect. Leave the pin electrically unconnected/isolated.
D2	NC	-	-	No connect. Leave the pin electrically unconnected/isolated.
D3	VDD25	-	Power	Positive supply for most of the logic function, including the processor core and most peripherals.
D10	VCCPHY	-	Power	VCC of the Ethernet PHY.
D11	VCCPHY	-	Power	VCC of the Ethernet PHY.
D12	PB1	I/O	TTL	GPIO port B bit 1.
D12 —	CCP2	I/O	TTL	Capture/Compare/PWM 2.
E1	PD4	I/O	TTL	GPIO port D bit 4.
E2	PD5	I/O	TTL	GPIO port D bit 5.

Table 16-5. Signals by Pin Number (continued)

Pin Number	Pin Name	Pin Type	Buffer Type <sup>a</sup>	Description
E3	LDO	-	Power	Low drop-out regulator output voltage. This pin requires an external capacitor between the pin and GND of 1 $\mu\text{F}$ or greater. When the on-chip LDO is used to provide power to the logic, the $_{\text{LDO}}$ pin must also be connected to the $_{\text{VDD25}}$ pins at the board level in addition to the decoupling capacitor(s).
E10	VDD33	-	Power	Positive supply for I/O and some logic.
E11	CMOD0	1	TTL	CPU Mode bit 0. Input must be set to logic 0 (grounded); other encodings reserved.
E12	PB0	I/O	TTL	GPIO port B bit 0.
E12	CCP0	I/O	TTL	Capture/Compare/PWM 0.
F1	PD7	I/O	TTL	GPIO port D bit 7.
[	C0o	0	TTL	Analog comparator 0 output.
F2	PD6	I/O	TTL	GPIO port D bit 6.
F3	VDD25	-	Power	Positive supply for most of the logic function, including the processor core and most peripherals.
F10	GND	-	Power	Ground reference for logic and I/O pins.
F11	GND	-	Power	Ground reference for logic and I/O pins.
F12	GND	-	Power	Ground reference for logic and I/O pins.
G1	PD0	I/O	TTL	GPIO port D bit 0.
G2	PD1	I/O	TTL	GPIO port D bit 1.
G3	VDD25	-	Power	Positive supply for most of the logic function, including the processor core and most peripherals.
G10	VDD33	-	Power	Positive supply for I/O and some logic.
G11	VDD33	-	Power	Positive supply for I/O and some logic.
G12	VDD33	-	Power	Positive supply for I/O and some logic.
H1	PD3	I/O	TTL	GPIO port D bit 3.
H2	PD2	I/O	TTL	GPIO port D bit 2.
H3	GND	-	Power	Ground reference for logic and I/O pins.
H10	VDD33	-	Power	Positive supply for I/O and some logic.
H11	RST	I	TTL	System reset input.
H12	PF1	I/O	TTL	GPIO port F bit 1.
J1	XTALNPHY	0	TTL	Ethernet PHY XTALN 25-MHz oscillator crystal output. Leave unconnected when using a single-ended 25-MHz clock input connected to the XTALPPHY pin.
J2	XTALPPHY	I	TTL	Ethernet PHY XTALP 25-MHz oscillator crystal input or external clock reference input.
J3	GND	-	Power	Ground reference for logic and I/O pins.
J10	GND	-	Power	Ground reference for logic and I/O pins.
144	PF2	I/O	TTL	GPIO port F bit 2.
J11 –	LED1	0	TTL	Ethernet LED 1.
140	PF3	I/O	TTL	GPIO port F bit 3.
J12	LED0	0	TTL	Ethernet LED 0.
K1	NC	-	-	No connect. Leave the pin electrically unconnected/isolated.
K2	NC	-	-	No connect. Leave the pin electrically unconnected/isolated.

Table 16-5. Signals by Pin Number (continued)

Pin Number	Pin Name	Pin Type	Buffer Type <sup>a</sup>	Description
K3	ERBIAS	ı	Analog	12.4-kΩ resistor (1% precision) used internally for Ethernet PHY.
K4	GNDPHY	-	Power	GND of the Ethernet PHY.
K5	GND	-	Power	Ground reference for logic and I/O pins.
K6	GND	-	Power	Ground reference for logic and I/O pins.
K7	VDD33	-	Power	Positive supply for I/O and some logic.
K8	VDD33	-	Power	Positive supply for I/O and some logic.
K9	VDD33	-	Power	Positive supply for I/O and some logic.
K10	GND	-	Power	Ground reference for logic and I/O pins.
K11	NC	-	-	No connect. Leave the pin electrically unconnected/isolated.
K12	NC	-	-	No connect. Leave the pin electrically unconnected/isolated.
L1	PC4	I/O	TTL	GPIO port C bit 4.
L2	NC	-	-	No connect. Leave the pin electrically unconnected/isolated.
	PA0	I/O	TTL	GPIO port A bit 0.
L3	U0Rx	1	TTL	UART module 0 receive. When in IrDA mode, this signal has IrDA modulation.
	PA3	I/O	TTL	GPIO port A bit 3.
L4	SSI0Fss	I/O	TTL	SSI module 0 frame.
	PA4	I/O	TTL	GPIO port A bit 4.
L5 –	SSIORx	I	TTL	SSI module 0 receive.
1.0	PA6	I/O	TTL	GPIO port A bit 6.
L6 –	CCP1	I/O	TTL	Capture/Compare/PWM 1.
L7	RXIN	- I	Analog	RXIN of the Ethernet PHY.
L8	TXON	0	Analog	TXON of the Ethernet PHY.
L9	MDIO	I/O	TTL	MDIO of the Ethernet PHY.
L10	GND	-	Power	Ground reference for logic and I/O pins.
L11	osc0	I	Analog	Main oscillator crystal input or an external clock reference input.
L12	VDD	-	Power	Positive supply for I/O and some logic.
	PC5	I/O	TTL	GPIO port C bit 5.
M1	C1+	I	Analog	Analog comparator 1 positive input.
	Clo	0	TTL	Analog comparator 1 output.
Ma	PC6	I/O	TTL	GPIO port C bit 6.
M2	CCP3	I/O	TTL	Capture/Compare/PWM 3.
	PA1	I/O	TTL	GPIO port A bit 1.
M3	U0Tx	0	TTL	UART module 0 transmit. When in IrDA mode, this signal has IrDA modulation.
MA	PA2	I/O	TTL	GPIO port A bit 2.
M4	SSI0Clk	I/O	TTL	SSI module 0 clock.
ME	PA5	I/O	TTL	GPIO port A bit 5.
M5	SSIOTx	0	TTL	SSI module 0 transmit.
M6	NC	-	-	No connect. Leave the pin electrically unconnected/isolated.
M7	RXIP	I	Analog	RXIP of the Ethernet PHY.
M8	TXOP	0	Analog	TXOP of the Ethernet PHY.

Table 16-5. Signals by Pin Number (continued)

Pin Number	Pin Name	Pin Type	Buffer Type <sup>a</sup>	Description
M9	PF0	I/O	TTL	GPIO port F bit 0.
M10	NC	-	-	No connect. Leave the pin electrically unconnected/isolated.
M11	OSC1	0	Analog Main oscillator crystal output. Leave unconnected when single-ended clock source.	
M12	NC	-	-	No connect. Leave the pin electrically unconnected/isolated.

a. The TTL designation indicates the pin has TTL-compatible voltage levels.

Table 16-6. Signals by Signal Name

Pin Name	Pin Number	Pin Type	Buffer Type <sup>a</sup>	Description
ADC0	B1	I	Analog	Analog-to-digital converter input 0.
ADC1	A1	I	Analog	Analog-to-digital converter input 1.
C0+	A7	1	Analog	Analog comparator 0 positive input.
C0-	A6	1	Analog	Analog comparator 0 negative input.
C0o	F1	0	TTL	Analog comparator 0 output.
C1+	M1	!	Analog	Analog comparator 1 positive input.
C1-	В7	1	Analog	Analog comparator 1 negative input.
Clo	M1	0	TTL	Analog comparator 1 output.
CCP0	E12	I/O	TTL	Capture/Compare/PWM 0.
CCP1	L6	I/O	TTL	Capture/Compare/PWM 1.
CCP2	D12	I/O	TTL	Capture/Compare/PWM 2.
CCP3	M2	I/O	TTL	Capture/Compare/PWM 3.
CMOD0	E11	I	TTL	CPU Mode bit 0. Input must be set to logic 0 (grounded); other encodings reserved.
CMOD1	B10	I	TTL	CPU Mode bit 1. Input must be set to logic 0 (grounded); other encodings reserved.
ERBIAS	K3	I	Analog	12.4-k $\Omega$ resistor (1% precision) used internally for Ethernet PHY.
GND	B6 C4 C5 F10 F11 F12 H3 J3 J10 K5 K6 K10 L10	-	Power	Ground reference for logic and I/O pins.
GNDA	A5 B5	-	Power	The ground reference for the analog circuits (ADC, Analog Comparators, etc.). These are separated from GND to minimize the electrical noise contained on VDD from affecting the analog functions.
GNDPHY	C8 C9 K4	-	Power	GND of the Ethernet PHY.

Table 16-6. Signals by Signal Name (continued)

Pin Name	Pin Number	Pin Type	Buffer Type <sup>a</sup>	Description	
LDO	E3	-	Power	Low drop-out regulator output voltage. This pin requires an external capacitor between the pin and GND of 1 $\mu$ F or greater. When the on-chip LDO is used to provide power to the logic, the LDO pin must also be connected to the VDD2: pins at the board level in addition to the decoupling capacitor(s).	
LED0	J12	0	TTL	Ethernet LED 0.	
LED1	J11	0	TTL	Ethernet LED 1.	
MDIO	L9	I/O	TTL	MDIO of the Ethernet PHY.	
NC	A2 A3 A4 A11 A12 B2 B3 B4 B11 B12 C1 C2 D1 D2 K1 K2 K11 K12 L2 M6 M10 M12	-	-	No connect. Leave the pin electrically unconnected/isolated.	
osc0	L11	I	Analog	Main oscillator crystal input or an external clock reference input.	
osc1	M11	0	Analog	Main oscillator crystal output. Leave unconnected when using a single-ended clock source.	
PA0	L3	I/O	TTL	GPIO port A bit 0.	
PA1	M3	I/O	TTL	GPIO port A bit 1.	
PA2	M4	I/O	TTL	GPIO port A bit 2.	
PA3	L4	I/O	TTL	GPIO port A bit 3.	
PA4	L5	I/O	TTL	GPIO port A bit 4.	
PA5	M5	I/O	TTL	GPIO port A bit 5.	
PA6	L6	I/O	TTL	GPIO port A bit 6.	
PB0	E12	I/O	TTL	GPIO port B bit 0.	
PB1	D12	I/O	TTL	GPIO port B bit 1.	
PB2	C11	I/O	TTL	GPIO port B bit 2.	
PB3	C12	I/O	TTL	GPIO port B bit 3.	
PB4	A6	I/O	TTL	GPIO port B bit 4.	
PB5	В7	I/O	TTL	GPIO port B bit 5.	
PB6	A7	I/O	TTL	GPIO port B bit 6.	
PB7	A8	I/O	TTL	GPIO port B bit 7.	

Table 16-6. Signals by Signal Name (continued)

Pin Name	Pin Number	Pin Type	Buffer Type <sup>a</sup>	Description	
PC0	A9	I/O	TTL	GPIO port C bit 0.	
PC1	В9	I/O	TTL	GPIO port C bit 1.	
PC2	B8	I/O	TTL	GPIO port C bit 2.	
PC3	A10	I/O	TTL	GPIO port C bit 3.	
PC4	L1	I/O	TTL	GPIO port C bit 4.	
PC5	M1	I/O	TTL	GPIO port C bit 5.	
PC6	M2	I/O	TTL	GPIO port C bit 6.	
PD0	G1	I/O	TTL	GPIO port D bit 0.	
PD1	G2	I/O	TTL	GPIO port D bit 1.	
PD2	H2	I/O	TTL	GPIO port D bit 2.	
PD3	H1	I/O	TTL	GPIO port D bit 3.	
PD4	E1	I/O	TTL	GPIO port D bit 4.	
PD5	E2	I/O	TTL	GPIO port D bit 5.	
PD6	F2	I/O	TTL	GPIO port D bit 6.	
PD7	F1	I/O	TTL	GPIO port D bit 7.	
PF0	M9	I/O	TTL	GPIO port F bit 0.	
PF1	H12	I/O	TTL	GPIO port F bit 1.	
PF2	J11	I/O	TTL	GPIO port F bit 2.	
PF3	J12	I/O	TTL	GPIO port F bit 3.	
RST	H11	I	TTL	System reset input.	
RXIN	L7	I	Analog	RXIN of the Ethernet PHY.	
RXIP	M7	I	Analog	RXIP of the Ethernet PHY.	
SSIOClk	M4	I/O	TTL	SSI module 0 clock.	
SSI0Fss	L4	I/O	TTL	SSI module 0 frame.	
SSI0Rx	L5	I	TTL	SSI module 0 receive.	
SSI0Tx	M5	0	TTL	SSI module 0 transmit.	
SWCLK	A9	I	TTL	JTAG/SWD CLK.	
SWDIO	В9	I/O	TTL	JTAG TMS and SWDIO.	
SWO	A10	0	TTL	JTAG TDO and SWO.	
TCK	A9	I	TTL	JTAG/SWD CLK.	
TDI	B8	I	TTL	JTAG TDI.	
TDO	A10	0	TTL	JTAG TDO and SWO.	
TMS	B9	I/O	TTL	JTAG TMS and SWDIO.	
TRST	A8	I	TTL	JTAG TRST.	
TXON	L8	0	Analog	TXON of the Ethernet PHY.	
TXOP	M8	0	Analog	TXOP of the Ethernet PHY.	
U0Rx	L3	I	TTL	UART module 0 receive. When in IrDA mode, this signal has IrDA modulation.	
UOTx	M3	0	TTL	UART module 0 transmit. When in IrDA mode, this signal has IrDA modulation.	

Table 16-6. Signals by Signal Name (continued)

Pin Name	Pin Number	Pin Type	Buffer Type <sup>a</sup>	Description
VCCPHY	C10 D10 D11	-	Power	VCC of the Ethernet PHY.
VDD	L12	-	Power	Positive supply for I/O and some logic.
VDD25	C3 D3 F3 G3	-	Power	Positive supply for most of the logic function, including the processor core and most peripherals.
VDD33	E10 G10 G11 G12 H10 K7 K8 K9	-	Power	Positive supply for I/O and some logic.
VDDA	C6 C7	-	Power	The positive supply (3.3 V) for the analog circuits (ADC, Analog Comparators, etc.). These are separated from VDD to minimize the electrical noise contained on VDD from affecting the analog functions. VDDA pins must be connected to 3.3 V, regardless of system implementation.
XTALNPHY	J1	0	TTL	Ethernet PHY XTALN 25-MHz oscillator crystal output. Leave unconnected when using a single-ended 25-MHz clock input connected to the XTALPPHY pin.
XTALPPHY	J2	I	TTL	Ethernet PHY XTALP 25-MHz oscillator crystal input or external clock reference input.

a. The TTL designation indicates the pin has TTL-compatible voltage levels.

Table 16-7. Signals by Function, Except for GPIO

Function	Pin Name	Pin Number	Pin Type	Buffer Type <sup>a</sup>	Description
ADC	ADC0	B1	I	Analog	Analog-to-digital converter input 0.
ADC	ADC1	A1	I	Analog	Analog-to-digital converter input 1.
	C0+	A7	I	Analog Analog comparator 0 positive input.	
	C0-	A6	I	Analog	Analog comparator 0 negative input.
Analog Comparators	C0o	F1	0	TTL	Analog comparator 0 output.
Analog Comparators	C1+	M1	I	Analog	Analog comparator 1 positive input.
	C1-	B7	I	Analog	Analog comparator 1 negative input.
	Clo	M1	0	TTL	Analog comparator 1 output.

Table 16-7. Signals by Function, Except for GPIO (continued)

Function	Pin Name	Pin Number	Pin Type	Buffer Type <sup>a</sup>	Description	
	ERBIAS	K3	I	Analog	12.4-k $\Omega$ resistor (1% precision) used internally for Ethernet PHY.	
	GNDPHY	C8 C9 K4	-	Power	GND of the Ethernet PHY.	
	LED0	J12	0	TTL	Ethernet LED 0.	
	LED1	J11	0	TTL	Ethernet LED 1.	
	MDIO	L9	I/O	TTL	MDIO of the Ethernet PHY.	
	RXIN	L7	I	Analog	RXIN of the Ethernet PHY.	
Eth a wa at	RXIP	M7	I	Analog	RXIP of the Ethernet PHY.	
Ethernet	TXON	L8	0	Analog	TXON of the Ethernet PHY.	
	TXOP	M8	0	Analog	TXOP of the Ethernet PHY.	
	VCCPHY	C10 D10 D11	-	Power	VCC of the Ethernet PHY.	
	XTALNPHY	J1	0	TTL	Ethernet PHY XTALN 25-MHz oscillator crystal output. Leave unconnected when using a single-ended 25-MHz clock input connected to the XTALPPHY pin.	
	XTALPPHY	J2	I	TTL	Ethernet PHY XTALP 25-MHz oscillator crystal input or external clock reference input.	
	CCP0	E12	I/O	TTL	Capture/Compare/PWM 0.	
General-Purpose	CCP1	L6	I/O	TTL	Capture/Compare/PWM 1.	
Timers	CCP2	D12	I/O	TTL	Capture/Compare/PWM 2.	
	CCP3	M2	I/O	TTL	Capture/Compare/PWM 3.	
	SWCLK	A9	I	TTL	JTAG/SWD CLK.	
	SWDIO	B9	I/O	TTL	JTAG TMS and SWDIO.	
	SWO	A10	0	TTL	JTAG TDO and SWO.	
JTAG/SWD/SWO	TCK	A9	I	TTL	JTAG/SWD CLK.	
J IAG/SVVD/SVVO	TDI	B8	I	TTL	JTAG TDI.	
	TDO	A10	0	TTL	JTAG TDO and SWO.	
	TMS	В9	I/O	TTL	JTAG TMS and SWDIO.	
	TRST	A8	I	TTL	JTAG TRST.	

Table 16-7. Signals by Function, Except for GPIO (continued)

Function	Pin Name	Pin Number	Pin Type	Buffer Type <sup>a</sup>	Description
	GND	B6 C4 C5 F10 F11 F12 H3 J3 J10 K5 K6 K10 L10	-	Power	Ground reference for logic and I/O pins.
	GNDA	A5 B5	-	Power	The ground reference for the analog circuits (ADC, Analog Comparators, etc.). These are separated from GND to minimize the electrical noise contained on VDD from affecting the analog functions.
Power	LDO	E3	-	Power	Low drop-out regulator output voltage. This pin requires an external capacitor between the pin and GND of 1 $\mu$ F or greater. When the on-chip LDO is used to provide power to the logic, the LDO pin must also be connected to the VDD25 pins at the board level in addition to the decoupling capacitor(s).
	VDD	L12	-	Power	Positive supply for I/O and some logic.
	VDD25	C3 D3 F3 G3	-	Power	Positive supply for most of the logic function, including the processor core and most peripherals.
	VDD33	E10 G10 G11 G12 H10 K7 K8 K9	-	Power	Positive supply for I/O and some logic.
	VDDA	C6 C7	-	Power	The positive supply (3.3 V) for the analog circuits (ADC, Analog Comparators, etc.). These are separated from VDD to minimize the electrical noise contained on VDD from affecting the analog functions. VDDA pins must be connected to 3.3 V, regardless of system implementation.
	SSI0Clk	M4	I/O	TTL	SSI module 0 clock.
SSI	SSI0Fss	L4	I/O	TTL	SSI module 0 frame.
331	SSI0Rx	L5	I	TTL	SSI module 0 receive.
	SSIOTx	M5	0	TTL	SSI module 0 transmit.

Table 16-7. Signals by Function, Except for GPIO (continued)

Function	Pin Name	Pin Number	Pin Type	Buffer Type <sup>a</sup>	Description
	CMOD0	E11	I	TTL	CPU Mode bit 0. Input must be set to logic 0 (grounded); other encodings reserved.
System Control & Clocks	CMOD1	B10	I	TTL CPU Mode bit 1. Input must be set to logic (grounded); other encodings reserved.	
	osc0	L11	I	Analog	Main oscillator crystal input or an external clock reference input.
	osc1	M11	0	Analog	Main oscillator crystal output. Leave unconnected when using a single-ended clock source.
	RST	H11	I	TTL	System reset input.
UART	U0Rx	L3	I	TTL	UART module 0 receive. When in IrDA mode, this signal has IrDA modulation.
OAIXI	UOTx	M3	0	TTL	UART module 0 transmit. When in IrDA mode, this signal has IrDA modulation.

a. The TTL designation indicates the pin has TTL-compatible voltage levels.

Table 16-8. GPIO Pins and Alternate Functions

10	Pin Number	Multiplexed Function	Multiplexed Function
PA0	L3	U0Rx	
PA1	M3	UOTx	
PA2	M4	SSI0Clk	
PA3	L4	SSI0Fss	
PA4	L5	SSI0Rx	
PA5	M5	SSI0Tx	
PA6	L6	CCP1	
PB0	E12	CCP0	
PB1	D12	CCP2	
PB2	C11		
PB3	C12		
PB4	A6	C0-	
PB5	B7	C1-	
PB6	A7	C0+	
PB7	A8	TRST	
PC0	A9	TCK	SWCLK
PC1	B9	TMS	SWDIO
PC2	B8	TDI	
PC3	A10	TDO	SWO
PC4	L1		
PC5	M1	C1+	Clo
PC6	M2	CCP3	
PD0	G1		
PD1	G2		
PD2	H2		
PD3	H1		

Table 16-8. GPIO Pins and Alternate Functions (continued)

10	Pin Number	Multiplexed Function	Multiplexed Function
PD4	E1		
PD5	E2		
PD6	F2		
PD7	F1	C0o	
PF0	M9		
PF1	H12		
PF2	J11	LED1	
PF3	J12	LED0	

## 16.3 Connections for Unused Signals

Table 16-9 on page 557 show how to handle signals for functions that are not used in a particular system implementation for devices that are in a 100-pin LQFP package. Two options are shown in the table: an acceptable practice and a preferred practice for reduced power consumption and improved EMC characteristics. If a module is not used in a system, and its inputs are grounded, it is important that the clock to the module is never enabled by setting the corresponding bit in the **RCGCx** register.

Table 16-9. Connections for Unused Signals (100-pin LQFP)

Function	Signal Name	Pin Number	Acceptable Practice	Preferred Practice
ADC	ADC0	1	NC	GNDA
	ADC1	2		
	ERBIAS	41	Connect to GND through 12.4-kΩ resistor.	Connect to GND through 12.4-kΩ resistor.
	GNDPHY	42	GND	GND
		85		
		86		
	MDIO <sup>a</sup>	58	NC	NC
	RXIN	37	NC	GND
Ethernet	RXIP	40	NC	GND
	TXON	46	NC	GND
	TXOP	43	NC	GND
	VCCPHY	36	VDD	VDD
		83		
		84		
	XTALNPHY <sup>a</sup>	17	NC	NC
	XTALPPHY <sup>a</sup>	16	NC	GND
GPIO	All unused GPIOs	-	NC	GND
No Connects	NC	-	NC	NC
	OSC0	48	NC	GND
System	OSC1	49	NC	NC
Control	RST	64	Pull up as shown in Figure 5-1 on page 165	Connect through a capacitor to GND as close to pin as possible

a. Note that the Ethernet PHY is powered up by default. The PHY cannot be powered down unless a clock source is provided and the MDIO pin is pulled up through a 10-k $\Omega$  resistor.

Table 16-10 on page 558 show how to handle signals for functions that are not used in a particular system implementation for devices that are in a 108-pin BGA package. Two options are shown in the table: an acceptable practice and a preferred practice for reduced power consumption and improved EMC characteristics. If a module is not used in a system, and its inputs are grounded, it is important that the clock to the module is never enabled by setting the corresponding bit in the **RCGCx** register.

Table 16-10. Connections for Unused Signals, 108-pin BGA

Function	Signal Name	Pin Number	Acceptable Practice	Preferred Practice
ADC	ADC0	B1	NC	GNDA
	ADC1	A1		
	ERBIAS	K3	Connect to GND through 12.4-kΩ resistor.	Connect to GND through $12.4$ -k $\Omega$ resistor.
	GNDPHY	C8	GND	GND
		C9		
		K4		
	MDIO <sup>a</sup>	L9	NC	NC
 	RXIN	L7	NC	GND
Ethernet	RXIP	M7	NC	GND
	TXON	L8	NC	GND
	TXOP	M8	NC	GND
	VCCPHY	C10	VDD	VDD
		D10		
		D11		
	XTALNPHY <sup>a</sup>	J1	NC	NC
	XTALPPHY <sup>a</sup>	J2	NC	GND
GPIO	All unused GPIOs	-	NC	GND
No Connects	NC	-	NC	NC
	OSC0	L11	NC	GND
System	OSC1	M11	NC	NC
Control	RST	H11	Pull up as shown in Figure 5-1 on page 165	Connect through a capacitor to GND as close to pin as possible

a. Note that the Ethernet PHY is powered up by default. The PHY cannot be powered down unless a clock source is provided and the MDIO pin is pulled up through a  $10-k\Omega$  resistor.

# 17 Operating Characteristics

**Table 17-1. Temperature Characteristics** 

Characteristic	Symbol	Value	Unit
Industrial operating temperature range	T <sub>A</sub>	-40 to +85	°C
Extended operating temperature range	T <sub>A</sub>	-40 to +105	°C
Unpowered storage temperature range	T <sub>S</sub>	-65 to +150	°C

#### **Table 17-2. Thermal Characteristics**

Characteristic	Symbol	Value	Unit
Thermal resistance (junction to ambient) <sup>a</sup>	$\Theta_{JA}$	32	°C/W
Junction temperature <sup>b</sup>	T <sub>J</sub>	$T_A + (P \cdot \Theta_{JA})$	°C

a. Junction to ambient thermal resistance  $\theta_{\text{JA}}$  numbers are determined by a package simulator.

Table 17-3. ESD Absolute Maximum Ratings<sup>a</sup>

Parameter Name	Min	Nom	Max	Unit
V <sub>ESDHBM</sub>	-	-	2.0	kV
V <sub>ESDCDM</sub>	-	-	1.0	kV
V <sub>ESDMM</sub>	-	-	100	V

a. All Stellaris parts are ESD tested following the JEDEC standard.

b. Power dissipation is a function of temperature.

## 18 Electrical Characteristics

#### 18.1 DC Characteristics

## 18.1.1 Maximum Ratings

The maximum ratings are the limits to which the device can be subjected without permanently damaging the device.

**Note:** The device is not guaranteed to operate properly at the maximum ratings.

**Table 18-1. Maximum Ratings** 

Characteristic <sup>a</sup>	Symbol	\	Unit	
ona acteristic	Syllibol	Min	Max	Oille
I/O supply voltage (V <sub>DD</sub> )	V <sub>DD</sub>	0	4	V
Core supply voltage (V <sub>DD25</sub> )	V <sub>DD25</sub>	0	3	V
Analog supply voltage (V <sub>DDA</sub> )	$V_{DDA}$	0	4	V
Ethernet PHY supply voltage (V <sub>CCPHY</sub> )	V <sub>CCPHY</sub>	0	4	V
Input voltage		-0.3	5.5	V
Input voltage for a GPIO configured as an analog input	$V_{IN}$	-0.3	V <sub>DD</sub> + 0.3	V
Maximum current per output pins	1	-	25	mA
Maximum input voltage on a non-power pin when the microcontroller is unpowered	V <sub>NON</sub>	-	300	mV

a. Voltages are measured with respect to GND.

**Important:** This device contains circuitry to protect the inputs against damage due to high-static voltages or electric fields; however, it is advised that normal precautions be taken to avoid application of any voltage higher than maximum-rated voltages to this high-impedance circuit. Reliability of operation is enhanced if unused inputs are

connected to an appropriate logic voltage level (for example, either GND or  $V_{DD}$ ).

## 18.1.2 Recommended DC Operating Conditions

For special high-current applications, the GPIO output buffers may be used with the following restrictions. With the GPIO pins configured as 8-mA output drivers, a total of four GPIO outputs may be used to sink current loads up to 18 mA each. At 18-mA sink current loading, the  $V_{OL}$  value is specified as 1.2 V. The high-current GPIO package pins must be selected such that there are only a maximum of two per side of the physical package or BGA pin group with the total number of high-current GPIO outputs not exceeding four for the entire package.

**Table 18-2. Recommended DC Operating Conditions** 

Parameter	Parameter Name	Min	Nom	Max	Unit
$V_{DD}$	I/O supply voltage	3.0	3.3	3.6	V
V <sub>DD25</sub>	Core supply voltage	2.25	2.5	2.75	V
$V_{DDA}$	Analog supply voltage	3.0	3.3	3.6	V
V <sub>CCPHY</sub>	Ethernet PHY supply voltage	3.0	3.3	3.6	V
V <sub>IH</sub>	High-level input voltage	2.0	-	5.0	V
V <sub>IL</sub>	Low-level input voltage	-0.3	-	1.3	V

Table 18-2. Recommended DC Operating Conditions (continued)

Parameter	Parameter Name	Min	Nom	Max	Unit		
V <sub>OH</sub>	High-level output voltage	2.4	-	-	V		
V <sub>OL</sub> <sup>a</sup>	Low-level output voltage	-	-	0.4	V		
	High-level source current, V <sub>OH</sub> =2.4 V						
I	2-mA Drive	2.0	-	-	mA		
Іон	4-mA Drive	4.0	-	-	mA		
	8-mA Drive	8.0	-	-	mA		
	Low-level sink current, V <sub>OL</sub> =0.4 V						
1	2-mA Drive	2.0	-	-	mA		
I <sub>OL</sub>	4-mA Drive	4.0	-	-	mA		
	8-mA Drive	8.0	-	-	mA		

a.  $V_{OL}$  and  $V_{OH}$  shift to 1.2 V when using high-current GPIOs.

## 18.1.3 On-Chip Low Drop-Out (LDO) Regulator Characteristics

**Table 18-3. LDO Regulator Characteristics** 

Parameter	Parameter Name	Min	Nom	Max	Unit
V <sub>LDOOUT</sub>	Programmable internal (logic) power supply output value	2.25	2.5	2.75	V
	Output voltage accuracy	-	2%	-	%
t <sub>PON</sub>	Power-on time	-	-	100	μs
t <sub>ON</sub>	Time on	-	-	200	μs
t <sub>OFF</sub>	Time off	-	-	100	μs
V <sub>STEP</sub>	Step programming incremental voltage	-	50	-	mV
C <sub>LDO</sub>	External filter capacitor size for internal power supply	1.0	-	3.0	μF

#### 18.1.4 **GPIO Module Characteristics**

**Table 18-4. GPIO Module DC Characteristics** 

Parameter	Parameter Name	Min	Nom	Max	Unit
R <sub>GPIOPU</sub>	GPIO internal pull-up resistor	50	-	110	kΩ
R <sub>GPIOPD</sub>	GPIO internal pull-down resistor	55	-	180	kΩ
I <sub>LKG</sub>	GPIO input leakage current <sup>a</sup>	-	-	2	μΑ

a. The leakage current is measured with GND or V<sub>DD</sub> applied to the corresponding pin(s). The leakage of digital port pins is measured individually. The port pin is configured as an input and the pullup/pulldown resistor is disabled.

#### 18.1.5 Power Specifications

The power measurements specified in the tables that follow are run on the core processor using SRAM with the following specifications (except as noted):

■ V<sub>DD25</sub> = 2.50 V

- V<sub>DDA</sub> = 3.3 V
- V<sub>DDPHY</sub> = 3.3 V
- Temperature = 25°C
- Clock Source (MOSC) =3.579545 MHz Crystal Oscillator
- Main oscillator (MOSC) = enabled
- Internal oscillator (IOSC) = disabled

**Table 18-5. Detailed Power Specifications** 

Parameter Parameter Name		Conditions	$V_{\rm DD}, V_{\rm DDA}, V_{\rm DDA}$		2.5	Unit	
			Nom	Max	Nom	Max	
	Run mode 1	V <sub>DD25</sub> = 2.50 V	48	pending <sup>a</sup>	64	pending <sup>a</sup>	mA
	(Flash loop)	Code= while(1){} executed out of Flash					
		Peripherals = All ON					
		System Clock = 25 MHz (with PLL)					
	Run mode 2	V <sub>DD25</sub> = 2.50 V	5	pending <sup>a</sup>	33	pending <sup>a</sup>	mA
	(Flash loop)	Code= while(1){} executed out of Flash					
		Peripherals = All OFF					
I <sub>DD_RUN</sub>		System Clock = 25 MHz (with PLL)					
	Run mode 1	V <sub>DD25</sub> = 2.50 V	48	pending <sup>a</sup>	56	pending <sup>a</sup>	mA
	(SRAM loop)	Code= while(1){} executed in SRAM					
		Peripherals = All ON					
		System Clock = 25 MHz (with PLL)					
	Run mode 2	V <sub>DD25</sub> = 2.50 V	5	pending <sup>a</sup>	26	pending <sup>a</sup>	mA
	(SRAM loop)	Code= while(1){} executed in SRAM					
		Peripherals = All OFF					
		System Clock = 25 MHz (with PLL)					
I <sub>DD_SLEEP</sub>	Sleep mode	V <sub>DD25</sub> = 2.50 V	5	pending <sup>a</sup>	12	pending <sup>a</sup>	mA
		Peripherals = All OFF					
		System Clock = 25 MHz (with PLL)					
I <sub>DD_DEEPSLEEP</sub>	Deep-Sleep mode	LDO = 2.25 V	4.6	pending <sup>a</sup>	0.21	pending <sup>a</sup>	mA
		Peripherals = All OFF					
		System Clock = IOSC30KHZ/64					

a. Pending characterization completion.

## **18.1.6** Flash Memory Characteristics

## **Table 18-6. Flash Memory Characteristics**

Parameter	Parameter Name	Min	Nom	Max	Unit
PE <sub>CYC</sub>	Number of guaranteed program/erase cycles before failure <sup>a</sup>	10,000	100,000	-	cycles

**Table 18-6. Flash Memory Characteristics (continued)** 

Parameter	Parameter Name	Min	Nom	Max	Unit
T <sub>RET</sub>	Data retention at average operating temperature of 85°C (industrial) or 105°C (extended)	10	-	-	years
T <sub>PROG</sub>	Word program time	20	-	-	μs
T <sub>ERASE</sub>	Page erase time	20	-	-	ms
T <sub>ME</sub>	Mass erase time	-	-	250	ms

a. A program/erase cycle is defined as switching the bits from 1 -> 0 -> 1.

#### 18.1.7 Ethernet Controller

Table 18-7. Ethernet Controller DC Characteristics


Parameter	Parameter Name	Value	Unit
R <sub>EBIAS</sub>	Value of the pull-down resistor on the ERBIAS pin	12.4K ± 1 %	Ω

## 18.2 AC Characteristics

#### 18.2.1 Load Conditions

Unless otherwise specified, the following conditions are true for all timing measurements. Timing measurements are for 4-mA drive strength.

Figure 18-1. Load Conditions



#### 18.2.2 Clocks

Table 18-8. Phase Locked Loop (PLL) Characteristics

Parameter Parameter Name		Min	Nom	Max	Unit
f <sub>ref_crystal</sub>	Crystal reference <sup>a</sup>	3.579545	-	8.192	MHz
f <sub>ref_ext</sub>	External clock reference <sup>a</sup>	3.579545	-	8.192	MHz
f <sub>pll</sub>	PLL frequency <sup>b</sup>	-	400	-	MHz
T <sub>READY</sub>	PLL lock time	-	-	0.5	ms

a. The exact value is determined by the crystal value programmed into the XTAL field of the **Run-Mode Clock Configuration** (RCC) register.

Table 18-9 on page 564 shows the actual frequency of the PLL based on the crystal frequency used (defined by the XTAL field in the **RCC** register).

b. PLL frequency is automatically calculated by the hardware based on the XTAL field of the RCC register.

Table 18-9. Actual PLL Frequency

XTAL	Crystal Frequency (MHz)	PLL Frequency (MHz)	Error
0x4	3.5795	400.904	0.0023%
0x5	3.6864	398.1312	0.0047%
0x6	4.0	400	-
0x7	4.096	401.408	0.0035%
0x8	4.9152	398.1312	0.0047%
0x9	5.0	400	-
0xA	5.12	399.36	0.0016%
0xB	6.0	400	-
0xC	6.144	399.36	0.0016%
0xD	7.3728	398.1312	0.0047%
0xE	8.0	400	0.0047%
0xF	8.192	398.6773333	0.0033%

**Table 18-10. Clock Characteristics** 

Parameter	Parameter Name	Min	Nom	Max	Unit
f <sub>IOSC</sub>	Internal 12 MHz oscillator frequency	8.4	12	15.6	MHz
f <sub>IOSC30KHZ</sub>	Internal 30 KHz oscillator frequency	15	30	45	KHz
f <sub>MOSC</sub>	Main oscillator frequency	1	-	8.192	MHz
t <sub>MOSC_per</sub>	Main oscillator period	125	-	1000	ns
f <sub>ref_crystal_bypass</sub>	Crystal reference using the main oscillator (PLL in BYPASS mode) <sup>a</sup>	1	-	8.192	MHz
f <sub>ref_ext_bypass</sub>	External clock reference (PLL in BYPASS mode) <sup>a</sup>	0	-	25	MHz
f <sub>system_clock</sub>	System clock	0	-	25	MHz

a. The ADC must be clocked from the PLL or directly from a 16-MHz clock source to operate properly.

**Table 18-11. Crystal Characteristics** 

Parameter Name		Va	lue		Units
Frequency	8	6	4	3.5	MHz
Frequency tolerance	±50	±50	±50	±50	ppm
Aging	±5	±5	±5	±5	ppm/yr
Oscillation mode	Parallel	Parallel	Parallel	Parallel	-
Temperature stability (-40°C to 85°C)	±25	±25	±25	±25	ppm
Temperature stability (-40°C to 105°C)	±25	±25	±25	±25	ppm
Motional capacitance (typ)	27.8	37.0	55.6	63.5	pF
Motional inductance (typ)	14.3	19.1	28.6	32.7	mH
Equivalent series resistance (max)	120	160	200	220	Ω
Shunt capacitance (max)	10	10	10	10	pF
Load capacitance (typ)	16	16	16	16	pF
Drive level (typ)	100	100	100	100	μW

## 18.2.2.1 System Clock Specifications with ADC Operation

Table 18-12. System Clock Characteristics with ADC Operation

	Parameter	Parameter Name	Min	Nom	Max	Unit
Г	f <sub>sysadc</sub>	System clock frequency when the ADC module is	16	-	-	MHz
		operating (when PLL is bypassed)				

## 18.2.3 JTAG and Boundary Scan

**Table 18-13. JTAG Characteristics** 

Parameter No.	Parameter	Parameter Name	Min	Nom	Max	Unit
J1	f <sub>TCK</sub>	TCK operational clock frequency	0	-	10	MHz
J2	t <sub>TCK</sub>	TCK operational clock period	100	-	-	ns
J3	t <sub>TCK_LOW</sub>	TCK clock Low time	-	t <sub>TCK</sub> /2	-	ns
J4	t <sub>TCK_HIGH</sub>	TCK clock High time	-	t <sub>TCK</sub> /2	-	ns
J5	t <sub>TCK_R</sub>	TCK rise time	0	-	10	ns
J6	t <sub>TCK_F</sub>	TCK fall time	0	-	10	ns
J7	t <sub>TMS_SU</sub>	TMS setup time to TCK rise	20	-	-	ns
J8	t <sub>TMS_HLD</sub>	TMS hold time from TCK rise	20	-	-	ns
J9	t <sub>TDI_SU</sub>	TDI setup time to TCK rise	25	-	-	ns
J10	t <sub>TDI_HLD</sub>	TDI hold time from TCK rise	25	-	-	ns
		2-mA drive		23	35	ns
J11	TCK fall to Data	4-mA drive	_	15	26	ns
t <sub>TDO_ZDV</sub>	Valid from High-Z	8-mA drive		14	25	ns
		8-mA drive with slew rate control		18	29	ns
		2-mA drive		21	35	ns
J12	TCK fall to Data Valid from Data	4-mA drive	_	14	25	ns
t <sub>TDO_DV</sub>	Valid	8-mA drive		13	24	ns
		8-mA drive with slew rate control		18	28	ns
		2-mA drive		9	11	ns
J13	тск fall to High-Z	4-mA drive	_	7	9	ns
t TDO_DVZ	from Data Valid	8-mA drive		6	8	ns
		8-mA drive with slew rate control		7	9	ns
J14	t <sub>TRST</sub>	TRST assertion time	100	-	-	ns
J15	t <sub>TRST_SU</sub>	TRST setup time to TCK rise	10	-	-	ns

Figure 18-2. JTAG Test Clock Input Timing




Figure 18-3. JTAG Test Access Port (TAP) Timing





Figure 18-4. JTAG TRST Timing



## 18.2.4 Reset

**Table 18-14. Reset Characteristics** 

Parameter No.	Parameter	Parameter Name	Min	Nom	Max	Unit
R1	V <sub>TH</sub>	Reset threshold	-	2.0	-	V
R2	V <sub>BTH</sub>	Brown-Out threshold	2.85	2.9	2.95	V
R3	T <sub>POR</sub>	Power-On Reset timeout	-	10	-	ms
R4	T <sub>BOR</sub>	Brown-Out timeout	-	500	-	μs
R5	T <sub>IRPOR</sub>	Internal reset timeout after POR	6	-	11	ms
R6	T <sub>IRBOR</sub>	Internal reset timeout after BOR <sup>a</sup>	0	-	1	μs

Table 18-14. Reset Characteristics (continued)

Parameter No.	Parameter	Parameter Name	Min	Nom	Max	Unit
R7	T <sub>IRHWR</sub>	Internal reset timeout after hardware reset (RST pin)	0	-	1	ms
R8	T <sub>IRSWR</sub>	Internal reset timeout after software-initiated system reset <sup>a</sup>	2.5	-	20	μs
R9	T <sub>IRWDR</sub>	Internal reset timeout after watchdog reset <sup>a</sup>	2.5	-	20	μs
R10	T <sub>VDDRISE</sub>	Supply voltage (V <sub>DD</sub> ) rise time (0V-3.3V)	-	-	100	ms
R11	T <sub>MIN</sub>	Minimum RST pulse width	2	-	-	μs

a. 20 \* t <sub>MOSC\_per</sub>

Figure 18-5. External Reset Timing (RST)




Figure 18-6. Power-On Reset Timing




Figure 18-7. Brown-Out Reset Timing




Figure 18-8. Software Reset Timing





Figure 18-9. Watchdog Reset Timing



## 18.2.5 Sleep Modes

Table 18-15. Sleep Modes AC Characteristics<sup>a</sup>

Parameter No	Parameter	Parameter Name	Min	Nom	Max	Unit
D1	t <sub>WAKE_S</sub>	Time to wake from interrupt in sleep or deep-sleep mode, not using the PLL	-	-	7	system clocks
D2	t <sub>WAKE_PLL_S</sub>	Time to wake from interrupt in sleep or deep-sleep mode when using the PLL	-	-	T <sub>READY</sub>	ms

a. Values in this table assume the IOSC is the clock source during sleep or deep-sleep mode.

## 18.2.6 General-Purpose I/O (GPIO)

Note: All GPIOs are 5 V-tolerant.

**Table 18-16. GPIO Characteristics** 

Parameter	Parameter Name	Condition	Min	Nom	Max	Unit
		2-mA drive		17	26	ns
	GPIO Rise Time (from 20% to 80%	4-mA drive	_	9	13	ns
GFION	of V <sub>DD</sub> )	8-mA drive	-	6	9	ns
		8-mA drive with slew rate control		10	12	ns
		2-mA drive		17	25	ns
	GPIO Fall Time (from 80% to 20%	4-mA drive		8	12	ns
GFIOI	of V <sub>DD</sub> )	8-mA drive	-	6	10	ns
		8-mA drive with slew rate control		11	13	ns


## 18.2.7 Analog-to-Digital Converter

Table 18-17. ADC Characteristics<sup>a</sup>

Parameter	Parameter Name	Min	Nom	Max	Unit
	Maximum single-ended, full-scale analog input voltage	-	-	3.0	V
V <sub>ADCIN</sub>	Minimum single-ended, full-scale analog input voltage	0.0	-	V	
	Maximum differential, full-scale analog input voltage	-	-	1.5	V
	Minimum differential, full-scale analog input voltage	0.0	-	-	V
N	Resolution		10		bits
f <sub>ADC</sub>	ADC internal clock frequency <sup>b</sup>	14	16	18	MHz
t <sub>ADCCONV</sub>	Conversion time <sup>c</sup>	4			μs
f ADCCONV	Conversion rate <sup>c</sup>		250		k samples/s
t <sub>LT</sub>	Latency from trigger to start of conversion	-	2	-	system clocks
IL	ADC input leakage	-	-	±3.0	μA
R <sub>ADC</sub>	ADC equivalent resistance	-	-	10	kΩ
C <sub>ADC</sub>	ADC equivalent capacitance	0.9	1.0	1.1	pF
EL	Integral nonlinearity error	-	-	±3	LSB
E <sub>D</sub>	Differential nonlinearity error	- ±2		LSB	
E <sub>O</sub>	Offset error	-	-	+6 <sup>d</sup>	LSB
E <sub>G</sub>	Full-scale gain error	-	-	±3	LSB
E <sub>TS</sub>	Temperature sensor accuracy	-	-	±5	°C

a. The ADC reference voltage is 3.0 V. This reference voltage is internally generated from the 3.3 VDDA supply by a band gap circuit.

Figure 18-10. ADC Input Equivalency Diagram



b. The ADC must be clocked from the PLL or directly from an external clock source to operate properly.

c. The conversion time and rate scale from the specified number if the ADC internal clock frequency is any value other than 16 MHz.

d. The offset error listed above is the conversion result with 0 V applied to the ADC input.

**Table 18-18. ADC Module Internal Reference Characteristics** 

Parameter	Parameter Name	Min	Nom	Max	Unit
V <sub>REFI</sub>	Internal voltage reference for ADC	-	3.0	-	V
E <sub>IR</sub>	Internal voltage reference error	-	-	±2.5	%


## 18.2.8 Synchronous Serial Interface (SSI)

**Table 18-19. SSI Characteristics** 

Parameter No.	Parameter	Parameter Name	Min	Nom	Max	Unit
S1	t <sub>clk_per</sub>	SSIClk cycle time	2	-	65024	system clocks
S2	t <sub>clk_high</sub>	SSIClk high time	-	0.5	-	t clk_per
S3	t <sub>clk_low</sub>	SSIC1k low time	-	0.5	-	t clk_per
S4	t <sub>clkrf</sub>	SSIClk rise/fall time <sup>a</sup>	-	6	10	ns
S5	t <sub>DMd</sub>	Data from master valid delay time	0	-	1	system clocks
S6	t <sub>DMs</sub>	Data from master setup time	1	-	-	system clocks
S7	t <sub>DMh</sub>	Data from master hold time	2	-	-	system clocks
S8	t <sub>DSs</sub>	Data from slave setup time	1	-	-	system clocks
S9	t <sub>DSh</sub>	Data from slave hold time	2	-	-	system clocks

a. Note that the delays shown are using 8-mA drive strength.

Figure 18-11. SSI Timing for TI Frame Format (FRF=01), Single Transfer Timing Measurement







Figure 18-12. SSI Timing for MICROWIRE Frame Format (FRF=10), Single Transfer





## 18.2.9 Ethernet Controller

Table 18-20. 100BASE-TX Transmitter Characteristics<sup>a</sup>

Parameter Name	Min	Nom	Max	Unit
Peak output amplitude	950	-	1050	mVpk
Output amplitude symmetry	98	-	102	%
Output overshoot	-	-	5	%
Rise/Fall time	3	-	5	ns
Rise/Fall time imbalance	-	-	500	ps

Table 18-20. 100BASE-TX Transmitter Characteristics (continued)

Parameter Name	Min	Nom	Max	Unit
Duty cycle distortion	-	-	-	ps
Jitter	-	-	1.4	ns

a. Measured at the line side of the transformer.

## Table 18-21. 100BASE-TX Transmitter Characteristics (informative)<sup>a</sup>

Parameter Name	Min	Nom	Max	Unit
Return loss	16	-	-	dB
Open-circuit inductance	350	-	-	μH

a. The specifications in this table are included for information only. They are mainly a function of the external transformer and termination resistors used for measurements.

#### Table 18-22. 100BASE-TX Receiver Characteristics

Parameter Name	Min	Nom	Max	Unit
Signal detect assertion threshold	600	700	-	mVppd
Signal detect de-assertion threshold	350	425	-	mVppd
Differential input resistance	-	20	-	kΩ
Jitter tolerance (pk-pk)	4	-	-	ns
Baseline wander tracking	-75	-	+75	%
Signal detect assertion time	-	-	1000	μs
Signal detect de-assertion time	-	-	4	μs

Table 18-23. 10BASE-T Transmitter Characteristics<sup>a</sup>

Parameter Name	Min	Nom	Max	Unit
Peak differential output signal	2.2	-	2.8	V
Harmonic content	27	-	-	dB
Link pulse width	-	100	-	ns
Start-of-idle pulse width	-	300	-	ns
		350		

a. The Manchester-encoded data pulses, the link pulse and the start-of-idle pulse are tested against the templates and using the procedures found in Clause 14 of *IEEE 802.3*.

Table 18-24. 10BASE-T Transmitter Characteristics (informative)<sup>a</sup>

Parameter Name	Min	Nom	Max	Unit
Output return loss	15	-	-	dB
Output impedance balance	29-17log(f/10)	-	-	dB
Peak common-mode output voltage	-	-	50	mV
Common-mode rejection	-	-	100	mV
Common-mode rejection jitter	-	-	1	ns

a. The specifications in this table are included for information only. They are mainly a function of the external transformer and termination resistors used for measurements.

Table 18-25. 10BASE-T Receiver Characteristics

Parameter Name	Min	Nom	Max	Unit
Jitter tolerance (pk-pk)	30	-	-	ns
Input squelched threshold	500	600	700	mVppd
Differential input resistance	-	20	-	kΩ
Common-mode rejection	25	-	-	V

Table 18-26. Isolation Transformers<sup>a</sup>

Name	Value	Condition
Turns ratio	1 CT : 1 CT	+/- 5%
Open-circuit inductance	350 uH (min)	@ 10 mV, 10 kHz
Leakage inductance	0.40 uH (max)	@ 1 MHz (min)
Inter-winding capacitance	25 pF (max)	
DC resistance	0.9 Ohm (max)	
Insertion loss	0.4 dB (typ)	0-65 MHz
HIPOT	1500	Vrms

a. Two simple 1:1 isolation transformers are required at the line interface. Transformers with integrated common-mode chokes are recommended for exceeding FCC requirements. This table gives the recommended line transformer characteristics.

**Note:** The 100Base-TX amplitude specifications assume a transformer loss of 0.4 dB. For the transmit line transformer with higher insertion losses, up to 1.2 dB of insertion loss can be compensated by selecting the appropriate setting in the Transmit Amplitude Selection (TXO) bits in the **MR19** register.

Table 18-27. Ethernet Reference Crystal<sup>a</sup>

Name	Value	Condition
Frequency	25.00000	MHz
Frequency tolerance	±50	PPM
Aging	±2	PPM/yr
Temperature stability (-40° to 85°)	±5	PPM
Temperature stability (-40° to 105°)	±5	PPM
Oscillation mode	Parallel resonance, fundamental mode	
Parameters at 25° C ±2° C; Drive level = 0.5 mW		
Drive level (typ)	50-100	μW
Shunt capacitance (max)	10	pF
Motional capacitance (min)	10	fF
Series resistance (max)	60	Ω
Spurious response (max)	> 5 dB below main within 500 kHz	

a. If the internal crystal oscillator is used, select a crystal that meets these specifications.

T<sub>clkhi</sub> T<sub>clklo</sub>

Figure 18-14. External XTLP Oscillator Characteristics

**Table 18-28. External XTLP Oscillator Characteristics** 

Parameter Name	Symbol	Min	Nom	Max	Unit
XTLN Input Low Voltage	XTLN <sub>ILV</sub>	-	-	0.8	-
XTLP Frequency <sup>a</sup>	XTLP <sub>f</sub>	-	25.0	-	-
XTLP Period <sup>b</sup>	T <sub>clkper</sub>	-	40	-	-
XTLP Duty Cycle	XTLP <sub>DC</sub>	40	-	60	%
		40		60	
Rise/Fall Time	T <sub>r</sub> , T <sub>f</sub>	-	-	4.0	ns
Absolute Jitter	T <sub>JITTER</sub>	-	-	0.1	ns

a. IEEE 802.3 frequency tolerance ±50 ppm.

## 18.2.10 Analog Comparator

**Table 18-29. Analog Comparator Characteristics** 

Parameter	Parameter Name	Min	Nom	Max	Unit
V <sub>OS</sub>	Input offset voltage	-	±10	±25	mV
V <sub>CM</sub>	Input common mode voltage range	0	-	V <sub>DD</sub> -1.5	V
C <sub>MRR</sub>	Common mode rejection ratio	50	-	-	dB
T <sub>RT</sub>	Response time	-	-	1	μs
T <sub>MC</sub>	Comparator mode change to Output Valid	-	-	10	μs

**Table 18-30. Analog Comparator Voltage Reference Characteristics** 

Parameter	Parameter Name	Min	Nom	Max	Unit
R <sub>HR</sub>	Resolution high range	-	V <sub>DD</sub> /31	-	LSB
R <sub>LR</sub>	Resolution low range	-	V <sub>DD</sub> /23	-	LSB
A <sub>HR</sub>	Absolute accuracy high range	-	-	±1/2	LSB
A <sub>LR</sub>	Absolute accuracy low range	-	-	±1/4	LSB

b. IEEE 802.3 frequency tolerance ±50 ppm.

## A Serial Flash Loader

#### A.1 Serial Flash Loader

The Stellaris® serial flash loader is a preprogrammed flash-resident utility used to download code to the flash memory of a device without the use of a debug interface. The serial flash loader uses a simple packet interface to provide synchronous communication with the device. The flash loader runs off the crystal and does not enable the PLL, so its speed is determined by the crystal used. The two serial interfaces that can be used are the UART0 and SSI0 interfaces. For simplicity, both the data format and communication protocol are identical for both serial interfaces.

#### A.2 Interfaces

Once communication with the flash loader is established via one of the serial interfaces, that interface is used until the flash loader is reset or new code takes over. For example, once you start communicating using the SSI port, communications with the flash loader via the UART are disabled until the device is reset.

#### A.2.1 UART

The Universal Asynchronous Receivers/Transmitters (UART) communication uses a fixed serial format of 8 bits of data, no parity, and 1 stop bit. The baud rate used for communication is automatically detected by the flash loader and can be any valid baud rate supported by the host and the device. The auto detection sequence requires that the baud rate should be no more than 1/32 the crystal frequency of the board that is running the serial flash loader. This is actually the same as the hardware limitation for the maximum baud rate for any UART on a Stellaris device which is calculated as follows:

Max Baud Rate = System Clock Frequency / 16

In order to determine the baud rate, the serial flash loader needs to determine the relationship between its own crystal frequency and the baud rate. This is enough information for the flash loader to configure its UART to the same baud rate as the host. This automatic baud-rate detection allows the host to use any valid baud rate that it wants to communicate with the device.

The method used to perform this automatic synchronization relies on the host sending the flash loader two bytes that are both 0x55. This generates a series of pulses to the flash loader that it can use to calculate the ratios needed to program the UART to match the host's baud rate. After the host sends the pattern, it attempts to read back one byte of data from the UART. The flash loader returns the value of 0xCC to indicate successful detection of the baud rate. If this byte is not received after at least twice the time required to transfer the two bytes, the host can resend another pattern of 0x55, 0x55, and wait for the 0xCC byte again until the flash loader acknowledges that it has received a synchronization pattern correctly. For example, the time to wait for data back from the flash loader should be calculated as at least 2\*(20(bits/sync)/baud rate (bits/sec)). For a baud rate of 115200, this time is 2\*(20/115200) or 0.35 ms.

#### A.2.2 SSI

The Synchronous Serial Interface (SSI) port also uses a fixed serial format for communications, with the framing defined as Motorola format with SPH set to 1 and SPO set to 1. See "Frame Formats" on page 437 in the SSI chapter for more information on formats for this transfer protocol. Like the UART, this interface has hardware requirements that limit the maximum speed that the SSI clock can run. This allows the SSI clock to be at most 1/12 the crystal frequency of the board running

the flash loader. Since the host device is the master, the SSI on the flash loader device does not need to determine the clock as it is provided directly by the host.

## A.3 Packet Handling

All communications, with the exception of the UART auto-baud, are done via defined packets that are acknowledged (ACK) or not acknowledged (NAK) by the devices. The packets use the same format for receiving and sending packets, including the method used to acknowledge successful or unsuccessful reception of a packet.

#### A.3.1 Packet Format

All packets sent and received from the device use the following byte-packed format.

```
struct
{
  unsigned char ucSize;
  unsigned char ucCheckSum;
  unsigned char Data[];
};
```

ucSize The first byte received holds the total size of the transfer including

the size and checksum bytes.

ucChecksum This holds a simple checksum of the bytes in the data buffer only.

The algorithm is Data[0]+Data[1]+...+ Data[ucSize-3].

Data This is the raw data intended for the device, which is formatted in

some form of command interface. There should be ucSize-2 bytes of data provided in this buffer to or from the device.

#### A.3.2 Sending Packets

The actual bytes of the packet can be sent individually or all at once; the only limitation is that commands that cause flash memory access should limit the download sizes to prevent losing bytes during flash programming. This limitation is discussed further in the section that describes the serial flash loader command, COMMAND\_SEND\_DATA (see "COMMAND\_SEND\_DATA (0x24)" on page 578).

Once the packet has been formatted correctly by the host, it should be sent out over the UART or SSI interface. Then the host should poll the UART or SSI interface for the first non-zero data returned from the device. The first non-zero byte will either be an ACK (0xCC) or a NAK (0x33) byte from the device indicating the packet was received successfully (ACK) or unsuccessfully (NAK). This does not indicate that the actual contents of the command issued in the data portion of the packet were valid, just that the packet was received correctly.

## A.3.3 Receiving Packets

The flash loader sends a packet of data in the same format that it receives a packet. The flash loader may transfer leading zero data before the first actual byte of data is sent out. The first non-zero byte is the size of the packet followed by a checksum byte, and finally followed by the data itself. There is no break in the data after the first non-zero byte is sent from the flash loader. Once the device communicating with the flash loader receives all the bytes, it must either ACK or NAK the packet to indicate that the transmission was successful. The appropriate response after sending a NAK to the flash loader is to resend the command that failed and request the data again. If needed, the host may send leading zeros before sending down the ACK/NAK signal to the flash loader, as the

flash loader only accepts the first non-zero data as a valid response. This zero padding is needed by the SSI interface in order to receive data to or from the flash loader.

#### A.4 Commands

The next section defines the list of commands that can be sent to the flash loader. The first byte of the data should always be one of the defined commands, followed by data or parameters as determined by the command that is sent.

### A.4.1 COMMAND\_PING (0X20)

This command simply accepts the command and sets the global status to success. The format of the packet is as follows:

```
Byte[0] = 0x03;
Byte[1] = checksum(Byte[2]);
Byte[2] = COMMAND_PING;
```

The ping command has 3 bytes and the value for COMMAND\_PING is 0x20 and the checksum of one byte is that same byte, making Byte[1] also 0x20. Since the ping command has no real return status, the receipt of an ACK can be interpreted as a successful ping to the flash loader.

### A.4.2 COMMAND\_GET\_STATUS (0x23)

This command returns the status of the last command that was issued. Typically, this command should be sent after every command to ensure that the previous command was successful or to properly respond to a failure. The command requires one byte in the data of the packet and should be followed by reading a packet with one byte of data that contains a status code. The last step is to ACK or NAK the received data so the flash loader knows that the data has been read.

```
Byte[0] = 0x03
Byte[1] = checksum(Byte[2])
Byte[2] = COMMAND_GET_STATUS
```

## A.4.3 COMMAND\_DOWNLOAD (0x21)

This command is sent to the flash loader to indicate where to store data and how many bytes will be sent by the COMMAND\_SEND\_DATA commands that follow. The command consists of two 32-bit values that are both transferred MSB first. The first 32-bit value is the address to start programming data into, while the second is the 32-bit size of the data that will be sent. This command also triggers an erase of the full area to be programmed so this command takes longer than other commands. This results in a longer time to receive the ACK/NAK back from the board. This command should be followed by a COMMAND\_GET\_STATUS to ensure that the Program Address and Program size are valid for the device running the flash loader.

The format of the packet to send this command is a follows:

```
Byte[0] = 11
Byte[1] = checksum(Bytes[2:10])
Byte[2] = COMMAND_DOWNLOAD
Byte[3] = Program Address [31:24]
Byte[4] = Program Address [23:16]
Byte[5] = Program Address [15:8]
Byte[6] = Program Address [7:0]
Byte[7] = Program Size [31:24]
```

```
Byte[8] = Program Size [23:16]
Byte[9] = Program Size [15:8]
Byte[10] = Program Size [7:0]
```

### A.4.4 COMMAND\_SEND\_DATA (0x24)

This command should only follow a COMMAND\_DOWNLOAD command or another COMMAND\_SEND\_DATA command if more data is needed. Consecutive send data commands automatically increment address and continue programming from the previous location. The caller should limit transfers of data to a maximum 8 bytes of packet data to allow the flash to program successfully and not overflow input buffers of the serial interfaces. The command terminates programming once the number of bytes indicated by the COMMAND\_DOWNLOAD command has been received. Each time this function is called it should be followed by a COMMAND\_GET\_STATUS to ensure that the data was successfully programmed into the flash. If the flash loader sends a NAK to this command, the flash loader does not increment the current address to allow retransmission of the previous data.

```
Byte[0] = 11
Byte[1] = checksum(Bytes[2:10])
Byte[2] = COMMAND_SEND_DATA
Byte[3] = Data[0]
Byte[4] = Data[1]
Byte[5] = Data[2]
Byte[6] = Data[3]
Byte[7] = Data[4]
Byte[8] = Data[5]
Byte[9] = Data[6]
Byte[10] = Data[7]
```

## A.4.5 COMMAND\_RUN (0x22)

This command is used to tell the flash loader to execute from the address passed as the parameter in this command. This command consists of a single 32-bit value that is interpreted as the address to execute. The 32-bit value is transmitted MSB first and the flash loader responds with an ACK signal back to the host device before actually executing the code at the given address. This allows the host to know that the command was received successfully and the code is now running.

```
Byte[0] = 7
Byte[1] = checksum(Bytes[2:6])
Byte[2] = COMMAND_RUN
Byte[3] = Execute Address[31:24]
Byte[4] = Execute Address[23:16]
Byte[5] = Execute Address[15:8]
Byte[6] = Execute Address[7:0]
```

### A.4.6 COMMAND\_RESET (0x25)

This command is used to tell the flash loader device to reset. This is useful when downloading a new image that overwrote the flash loader and wants to start from a full reset. Unlike the COMMAND\_RUN command, this allows the initial stack pointer to be read by the hardware and set up for the new code. It can also be used to reset the flash loader if a critical error occurs and the host device wants to restart communication with the flash loader.

```
Byte[0] = 3
Byte[1] = checksum(Byte[2])
Byte[2] = COMMAND_RESET
```

The flash loader responds with an ACK signal back to the host device before actually executing the software reset to the device running the flash loader. This allows the host to know that the command was received successfully and the part will be reset.

# B Register Quick Reference

31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16
15	14	13	12	11	10	9	8	7	6	5	4	3	2	1	0
	rtex-M3														
หบ, type F	R/W, , reset	- (see page	e 51)				D./	ΛΤΛ							
								ATA ATA							
R1 type F	R/W, , reset	- (see nage	- 51)				Dr.								
ici, type i	( vv, , reset	- (acc page	551)				D.A	ATA							
								ATA							
R2, type F	R/W, , reset	- (see page	e 51)												
							DA	ATA							
							DA	ATA							
R3, type F	R/W, , reset	- (see page	e 51)												
							DA	ATA							
							DA	ATA							
R4, type F	R/W, , reset	- (see page	e 51)												
								ATA							
			54)				DA	ATA							
Ko, type F	R/W, , reset	- (see page	e 51)				D./	ATA							
								ATA							
R6, type F	R/W, , reset	- (see page	e 51)												
, 3,60		(555 pag	/				DA	ATA							
								ATA							
R7, type F	R/W, , reset	- (see page	e 51)												
							DA	ATA							
							DA	ATA							
R8, type F	R/W, , reset	- (see page	e 51)												
								ATA							
							DA	ATA							
R9, type F	R/W, , reset	- (see page	e 51)												
								ATA							
D40 4	D/M ====	. (occ = :	70 F1\				U.F	ATA							
K IU, type	R/W, , rese	ı (see pa	ye 51)				D/	ATA							
								ATA							
R11, type	R/W, , rese	t - (see pad	ge 51)												
,,,,	.,	, p = c	- ,				D.A	ATA							
							DA	ATA							
R12, type	R/W, , rese	t - (see pa	ge 51)												
								ATA							
							DA	ATA							
SP, type F	R/W, , reset	- (see page	e 52)												
								SP							
ID:	200	0.555	/	50'				SP							
LR, type I	≺/W, , reset	UXFFFF.FF	FFF (see pag	ge 53)				NIZ							
								NK NK							
PC type !	R/W, , reset	- (see nage	e 54)				LI	NIX.							
. c, type i	, reset	- (see pag	C 34)				Б	rC							
								C							
							•								

31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16
15	14	13	12	11	10	9	8	7	6	5	4	3	2	1	0
PSR, type	e R/W, , rese	et 0x0100.0	0000 (see pa	I ige 55)											
N	Z	С	V	Q	ICI	/ IT	THUMB								
		ICI	/ IT									ISR	NUM		1
PRIMASK	K, type R/W,	, reset 0x0	0000.0000 (s	see page 59	9)										
															PRIMASK
FAULTMA	ASK, type R	/W, , reset	0x0000.000	0 (see page	e 60)										
															FAULTMAS
BASEPRI	I, type R/W,	, reset 0x0	000.0000 (s	ee page 61	)										
									BASEPRI						
CONTRO	L, type R/W	, , reset 0x	0000.0000 (	see page 6	2)										
														ASP	TMPL
	-M3 Perip														
	n Timer (		) Registe	ers											
	E000.E000														
STCTRL,	type R/W, o	ffset 0x01	0, reset 0x0	000.0000											
															COUNT
					_								CLK_SRC	INTEN	ENABLE
STRELOA	AD, type R/V	V, offset 02	k014, reset	0x0000.000	)O										
							DEL	240			REL	.OAD			
OTOUDD	ENT 4 D	040 - FF	. 0040	-4.00000	0000		REL	JAD							
SICUKKI	ENT, type R	wc, onse	t uxu18, res	et uxuuuu.	0000						CLID	DENT			
							CURF	DENIT			CUR	RENT			
01	M0 D						00111	XLIVI							
Nested	-M3 Perip I Vectore E000.E000	d Interru	ıpt Conti	roller (N	VIC) Reg	gisters									
	R/W, offset		sat OvOOOO	0000											
Lito, type	7 10 11, 01136	0 0 100, 10	361 020000.	0000			IN	т							
							IN								
EN1. type	R/W, offset	t 0x104. re	set 0x0000.	0000											
	, , , , , , ,	,,,,													
									IN	IT		I			
DIS0, type	e R/W, offse	t 0x180, re	eset 0x0000	.0000											
							IN	Т							
							IN								
DIS1, type	e R/W, offse	t 0x184, re	eset 0x0000	.0000											
									IN	IT					
PEND0, ty	ype R/W, off	set 0x200	reset 0x00	00.000											
							IN	Т							
							IN	Т							
PEND1, ty	ype R/W, off	set 0x204	reset 0x00	00.000											
									IN	IT					
UNPEND	0, type R/W,	offset 0x2	280, reset 0	k0000.0000	)										
							IN	Т							
							IN	_							

24	20	20	20	27	26	25	24	1 22	22	24	20	10	10	17	16
31 15	30 14	29 13	28 12	27 11	26 10	25 9	24 8	23 7	22 6	21 5	20	19 3	18	17	16 0
				x0000.0000	10	3	0	,	· ·	3	T -			'	0
ON LIND	, type tave,	, onset oxz	.04, 16361 0.												
									IN	JT					
ACTIVE0. 1	type RO. o	ffset 0x300	), reset 0x0	000.0000											
71011120,	.,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,		,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,					NT							
								NT							
ACTIVE1.	type RO. o	ffset 0x304	l. reset 0x0	000.000											
	· <b>,</b> p · · · · · ·		,												
									IN	NT.					
PRI0, type	R/W, offse	et 0x400, re	set 0x0000	.0000											
	INTD								INTC						
	INTB								INTA						
PRI1, type	R/W, offse	et 0x404, re	set 0x0000	.0000											
	INTD								INTC						
	INTB								INTA						
PRI2, type	R/W, offse	et 0x408, re	set 0x0000	.0000											
	INTD	-							INTC						
	INTB								INTA						
PRI3, type	R/W, offse	et 0x40C, re	eset 0x0000	0.0000											
	INTD								INTC						
	INTB								INTA						
PRI4, type	R/W, offse	et 0x410, re	set 0x0000	.0000											
	INTD								INTC						
	INTB								INTA						
PRI5, type	R/W, offse	et 0x414, re	set 0x0000	.0000											
	INTD								INTC						
	INTB								INTA						
PRI6, type	R/W, offse	et 0x418, re	set 0x0000	.0000											
	INTD								INTC						
	INTB								INTA						
PRI7, type	R/W, offse	et 0x41C, re	eset 0x0000	0.0000											
	INTD								INTC						
	INTB								INTA						
PRI8, type	R/W, offse	et 0x420, re	set 0x0000	.0000				•							
	INTD								INTC						
	INTB								INTA						
PRI9, type	R/W, offse	et 0x424, re	set 0x0000	.0000											
	INTD								INTC						
	INTB								INTA						
PRI10, typ	e R/W, offs	set 0x428, r	eset 0x000	0.0000											
	INTD								INTC						
	INTB								INTA						
SWTRIG, t	ype WO, o	ffset 0xF00	), reset 0x0	000.0000											
												IN	TID		
Cortex-l	M3 Peri	oherals													
System Base 0xE	Control	Block (	SCB) Re	gisters											
CPUID, typ	e RO, offs	et 0xD00, r	reset 0x411	F.C231											
				ИP					VA	AR .			C	ON	
					PAF	RTNO		1					R	EV	

31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16
15	14	13	12	11	10	9	8	7	6	5	4	3	2	1	0
	type R/W,	offset 0xD0										1			
NMISET			PENDSV	UNPENDSV	PENDSTSET	PENDSTCLR		ISRPRE	ISRPEND					VEC	PEND
		PEND		RETBASE								VEC	CACT		
VTABLE, 1	type R/W, c	offset 0xD0	8, reset 0x(	0000.0000											
		BASE							OFFSET						
			OFF	SET											
APINT, typ	oe R/W, off	set 0xD0C,	reset 0xFA	05.0000											
							VECT	ΓΚΕΥ							
ENDIANESS						PRIGROUP	)						SYSRESREQ	VECTCLRACT	VECTRESE
SYSCTRL	, type R/W,	offset 0xD	10, reset 0	x0000.0000											
											SEVONPEND		SLEEPDEEP	SLEEPEXIT	
CFGCTRL	, type R/W	, offset 0xD	14, reset 0	x0000.0000	)										
						STKALIGN	BFHFNMIGN				DIV0	UNALIGNED		MAINPEND	BASETHE
SYSPRI1,	type R/W,	offset 0xD1	8, reset 0x	0000.0000											
									USAGE						
	BUS								MEM						
SYSPRI2,	type R/W,	offset 0xD1	C, reset 0x	0000.0000											
	SVC														
SYSPRI3.	type R/W.	offset 0xD2	0. reset 0x	0000.0000											
	TICK		.,						PENDSV						
									DEBUG						
SASHNUC	TPI type	R/W, offset	0vD24 res	eet OvOOOO	0000				52500						
OTOTINE	TIKE, type	Tavi, onset	0.0024, 16.		0000								USAGE	BUS	MEM
SVC	BUSP	MEMP	USAGEP	TICK	PNDSV		MON	SVCA				USGA	USAGE	BUSA	MEMA
							IVIOIN	SVCA				USGA		BOSA	IVILIVIA
FAULISIA	AI, type K/	N1C, offset	UXD28, res	set uxuuuu.	0000	DII /0						Lucon	1111/120	15.15 (0.7.4.7.	LINIBEE
DEADY/			DOTKE	DUOTKE	IMPDE	DIV0	UNALIGN	MANAA DV			MOTIVE	NOCP	INVPC	INVSTAT	UNDEF
BFARV			BSTKE	BUSTKE	IMPRE	PRECISE	IBUS	MMARV			MSTKE	MUSTKE		DERR	IERR
		k/W1C, offs	et 0xD2C, i	eset 0x000	0.0000							ı			
DBG	FORCED														
														VECT	
MMADDR	, type R/W,	offset 0xD	34, reset -												
							AD								
							AD	DR							
FAULTAD	DR, type R	/W, offset 0	xD38, rese	t -											
							AD								
							AD	DR							
Cortex-	M3 Peri	pherals													
Memory	y Protec	tion Unit	(MPU)	Register	s										
Base 0xE	E000.E000	)		-											
MPUTYPE	type RO,	offset 0xD9	90, reset 0	0000.0800											
											IRE	SION			
			DRE	GION											SEPARATE
MPUCTRL	, type R/W	, offset 0xD	94, reset 0	×0000.0000	)										
													PRIVDEFEN	HFNMIENA	ENABI F
MPHNHM	BER type	R/W, offset	OxD98 ros	et Oxonon (	2000										
GROWII	Lix, type	ort, onset	UADJU, 188		,,,,,,										
														NUMBER	
														NUMBER	

04	20	00	00	0.7	00	05	0.4	00	00	04	00	40	40	47	40
31 15	30 14	29 13	28 12	27 11	26 10	25 9	24 8	23 7	22 6	21 5	20 4	19	18	17	16 0
	E, type R/W							,	ŭ		_			<u> </u>	
IIII ODAOL	_, type 1011	, onoce oxe	300, 10001	0,0000.000			AD	DR							
					ADDR		,,,,				VALID			REGION	
MPUBASE	E1, type R/V	V. offset 0x	DA4. reset	0x0000.00											
	7.31.	,	,				AD	DR							
					ADDR						VALID			REGION	
MPUBASE	E2, type R/V	V, offset 0x	DAC, rese	t 0x0000.0	000										
							AD	DR							
					ADDR						VALID			REGION	
MPUBASE	E3, type R/V	V, offset 0x	DB4, reset	0x0000.00	000										
							AD	DR							
					ADDR						VALID			REGION	
MPUATTR	R, type R/W,	offset 0xD	A0, reset 0	0x0000.000	0										
			XN			AP					TEX		S	С	В
			SF	RD								SIZE			ENABLE
MPUATTR	R1, type R/V	V, offset 0x	DA8, reset	0x0000.00	00										
			XN			AP					TEX		S	С	В
			SF	RD								SIZE			ENABLE
MPUATTR	R2, type R/V	V, offset 0x	DB0, reset	0x0000.00	00										
			XN			AP					TEX		S	С	В
			SF	RD								SIZE			ENABLE
MPUATTR	R3, type R/V	V, offset 0x	DB8, reset	0x0000.00	00										
			XN			AP					TEX		S	С	В
			SF	RD								SIZE			ENABLE
-	Control 400F.E000														
DID0, type	e RO, offset	0x000, res	set - (see pa	age 177)											
		VER									CL	ASS			
			MA	JOR							MIM	NOR			
PBORCTL	, type R/W,	offset 0x0	30, reset 0	x0000.7FF	D (see page	179)									
														BORIOR	
LDOPCTL	., type R/W,	offset 0x0	34, reset 0x	×0000.0000	(see page	180)									
												VA	\DJ		
RIS, type	RO, offset (	0x050, rese	et 0x0000.0	<b>000</b> (see pa	age 181)										
									DI I I DIO					DODDIO	
IMC to	DAN -#-	0.054 =	-4 0-2000	0000 /	2000 (00)				PLLLRIS					BORRIS	
iwic, type	R/W, offset	uxu54, res	set uxuuu0.	ບບບບ (see   	page 182)										
									PLLLIM					BORIM	
MISC 4	e R/W1C, o	ffeet nener	reent five	000 0000 /	see page 15	33)			FLLLIIVI					BORIN	
инос, тур	e RIVVIC, O	iisel UXUSC	, reset uxu		see page 18	JJ)									
									PLLLMIS					BORMIS	
RESC tvn	oe R/W, offs	et 0x05C	reset - (see	nage 184)					. LLLIVIIO					DOMINIO	
, typ	, Oils	,	3001 (300	 											
											SW	WDT	BOR	POR	EXT
RCC. type	R/W, offse	t 0x060. re	set 0x0780	.3AD1 (see	page 185)							1			
, ., po	, 030			ACG	,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,		SDIV		USESYSDIV						
		PWRDN		BYPASS			XT	AL	/	OSC	SRC			IOSCDIS	MOSCDIS
PLLCFG. 1	type RO, of	fset 0x064	, reset - (se	e page 189	9)										
PLLCFG,	type RO, of	fset 0x064	, reset - (se	ee page 189	<del>)</del> )										

31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16
15	14	13	12	11	10	9	8	7	6	5	4	3	2	1	0
	oe R/W, offs	set 0x070, r	eset 0x078	<b>0.2810</b> (see					1						
USERCC2		DIA/DDAIO		BYPASS2	SYS	DIV2				0000000					
201 201 14	(050.4	PWRDN2				100)				OSCSRC2					
DSLPCLK	CFG, type	R/W, offset	0x144, res	et 0x0780.					1			I			
					DSDIV	ORIDE				DEOCCEDO	<u> </u>				
DID4 to	. DO -ff	4.0004	-4 /	100)						DSOSCSRO	,				
иит, туре		t 0x004, res	set - (see pa	age 193)		<b>NA</b>					DAD	TNO			
	PINCOUN	ER r			F/	AM			TEMP			KG	ROHS	OI	JAL
		t 0x008, res	ot 0v007E 0	102E (see n	age 105)				I LIVII				ROTIO	QC	<i>-</i>
DC0, type	KO, Olisei	UXUUU, TES	et 0x0071.0	1021 (See p	age 195)		CDA	MSZ							
								SHSZ							
DC1 type	PO offeet	0x010, res	et 0v0001 7	71RF (\$00 r	nage 196)		1 27 %	51102							
DO1, type	10, 011361	0.0010, 163	51 0X000 1.7	101 (300)	lage 150)										ADC
	MINS	YSDIV				IAXAM	DCSPD	MPU		TEMPSNS	PLL	WDT	SWO	SWD	JTAG
DC2, type		0x014, res	et 0x0307 (	0011 (see n	age 198)			0				1	2.10	5.16	11110
<b>Вог</b> , турс	110, 01100	0,014,100	OL 0X0001.0	(300 p	ugo 100)	COMP1	COMP0						TIMER2	TIMER1	TIMER0
						331411	COIVII O				SSI0			····	UART0
DC3, type	RO. offset	0x018, res	et 0x8F03 (	FC0 (see r	page 200)						- 3.0				
32KHZ	, 011361			CCP3	CCP2	CCP1	CCP0							ADC1	ADC0
OZIVIZ				C10		C1MINUS	C00	COPLUS	COMINUS					71801	71000
DC4. type	RO offset	0x01C, res	et 0x5000.0					1							
, . <b>, ,</b>	EPHY0		EMAC0	(000)	/ugo 202/										
			2113 100						GPIOG	GPIOF	GPIOE	GPIOD	GPIOC	GPIOB	GPIOA
RCGC0. tv	vpe R/W. o	ffset 0x100,	reset 0x00	l 1000040 (se	e page 204	1)									
, .,	,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,				- p-9										ADC
						MAXAI	DCSPD					WDT			
SCGC0. tv	vpe R/W. of	ffset 0x110,	reset 0x00	000040 (se	e page 206	j)						l			
		,			1,131	,									ADC
						MAXAI	DCSPD					WDT			
DCGC0. tv	vpe R/W. o	ffset 0x120,	reset 0x00	l	ee page 208	3)						l			
				`											ADC
												WDT			
RCGC1, tv	ype R/W, o	ffset 0x104,	reset 0x00	l 1000000 (se	ee page 210	))						l			
, -,	, ,				, 3.	COMP1	COMP0						TIMER2	TIMER1	TIMERO
							,				SSI0				UART0
SCGC1, ty	ype R/W, o	ffset 0x114,	reset 0x00	000000 (se	e page 212	2)					1				
						COMP1	COMP0						TIMER2	TIMER1	TIMER0
											SSI0				UART0
DCGC1, ty	ype R/W, o	ffset 0x124,	reset 0x00	000000 (se	ee page 214	1)					<u> </u>				-
		,		,,,,	. •	COMP1	COMP0						TIMER2	TIMER1	TIMERO
											SSI0				UART0
RCGC2, tv	ype R/W, o	ffset 0x108,	reset 0x00	000000 (se	ee page 216	3)					1				
	EPHY0	,	EMAC0	,											
									GPIOG	GPIOF	GPIOE	GPIOD	GPIOC	GPIOB	GPIOA
SCGC2, tv	ype R/W, o	ffset 0x118,	reset 0x00	000000 (se	e page 218	3)						I.		1	
, ,	EPHY0	-,	EMAC0	(-	. 5.										
									GPIOG	GPIOF	GPIOE	GPIOD	GPIOC	GPIOB	GPIOA
DCGC2. tv	ype R/W. o	ffset 0x128,	reset 0x00	1000000 (se	ee page 220	0)						I		1	
, •,	EPHY0	, , , , , , , , , , , , , ,	EMAC0		F 30 ZZ	,									
									GPIOG	GPIOF	GPIOE	GPIOD	GPIOC	GPIOB	GPIOA
									5. 100	5. 101	J. 10L	J 0. 10B	5. 100	0. 100	J. 10A

31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16
15	14	13	12	11	10	9	8	7	6	5	4	3	2	1	0
SRCR0, ty	ype R/W, of	fset 0x040	, reset 0x00	000000 (se	e page 222	)									
															ADC
												WDT			
SRCR1, ty	ype R/W, of	tset 0x044	, reset 0x00	1 <b>000000</b> (se	e page 223		COMPO	1				1	TIMEDO	TIMEDA	TIMEDO
						COMP1	COMP0				SSI0		TIMER2	TIMER1	UART0
SPCP2 fo	ype R/W, of	feat 0v048	rosot OvOC	000000 (se	ne page 224	\					3310				UAITIU
SKCKZ, tj	EPHY0	1561 02040	EMAC0		e page 224	,									
	LITTIO		LIVIAGO						GPIOG	GPIOF	GPIOE	GPIOD	GPIOC	GPIOB	GPIOA
Interna	l Memor	v			<u> </u>	<u> </u>									
Flash M	<b>/lemory (</b> 400F.D000	Control	Register	s (Flash	Control	Offset)									
FMA, type	e R/W, offse	et 0x000, re	set 0x0000	.0000											
															OFFSET
							OFF	SET							
FMD, type	e R/W, offse	et 0x004, re	set 0x0000	.0000											
								ATA							
							DA	ATA							
FMC, type	e R/W, offse	et 0x008, re	eset 0x0000	.0000											
				ı			WR	KEY							
												COMT	MERASE	ERASE	WRITE
FCRIS, ty	pe RO, offs	et 0x00C, i	reset 0x000	0.0000											
														DDIO	ADIO
FCIM to an	- D/W -ff-	-4.0+040 ==												PRIS	ARIS
FCIIVI, typ	e R/W, offs	et uxuru, r	eset uxuuui	J.0000											
														PMASK	AMASK
FCMISC 1	type R/W10	: offset 0x	014 reset (	X0000 000	n									1 WINTOIN	7 (10)7 (0)1
	.,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,	, 0.11001 0.11	.,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,												
														PMISC	AMISC
Interna	l Memor	v		l											
	lemory l	-	on Regis	ters (Sv	stem Co	ntrol Of	fset)								
	400F.E000		Jii itogio	tors (o)	310111 00		1001,								
USECRL,	type R/W, o	offset 0x14	0, reset 0x	18											
											US	SEC			ı
FMPRE0,	type R/W, o	offset 0x13	0 and 0x20	0, reset 0xl	FFFF.FFFF										
							READ_I	ENABLE							
							READ_I	ENABLE							
FMPPE0,	type R/W, o	offset 0x13	4 and 0x40	0, reset 0xF	FFF.FFFF										
							PROG_	ENABLE							
							PROG_	ENABLE							
	3G, type R/\	W, offset 0	x1D0, reset	0xFFFF.FF	FE										
NW								DATA							
						DA	ATA							DBG1	DBG0
	EG0, type R	/W, offset (	0x1E0, rese	t 0xFFFF.F	FFF			D							
NW								DATA							
HEED DE	-C4 4	//A/ -55	Dv4E4	4 Overer =			DA	ATA							
	EG1, type R	/vv, offset (	∪x1E4, rese	t UXFFFF.F	FFF			DATA							
NW							L.	DATA							
							DA	NIA							

31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16
15	14	13	12	11	10	9	8	7	6	5	4	3	2	1	0
MPRE1, 1	type R/W, c	offset 0x204	I, reset 0x0	000.FFFF								1			
							READ_	ENABLE							
							READ_	ENABLE							
MPRE2, 1	type R/W, c	offset 0x208	3, reset 0x0	000.0000											
							READ_	ENABLE							
							READ_	ENABLE							
MPRE3, 1	type R/W, c	offset 0x200	C, reset 0x0	0000.0000											
							READ_	ENABLE							
							READ_	ENABLE							
FMPPE1, t	type R/W, o	ffset 0x404	l, reset 0x0	000.FFFF											
							PROG_	ENABLE							
							PROG_	ENABLE							
MPPE2, t	type R/W, o	ffset 0x408	3, reset 0x0	000.0000											
								ENABLE							
							PROG_	ENABLE							
MPPE3, t	type R/W, o	offset 0x400	C, reset 0x0	000.0000											
								ENABLE							
				(GPIOs)			PROG_	ENABLE							
SPIO Poi	rt G base:	0x4002.50 0x4002.6 //, offset 0x0	000	x0000.0000	) (see page	263)									
											D	ATA			
SPIODIR,	type R/W,	offset 0x400	0, reset 0x0	0000.0000 (	see page 2	64)									
												IR			
SPIOIS, ty	pe R/W, of	fset 0x404,	reset 0x00	00.0000 (se	ee page 265	5)									
												IS			
SPIOIBE,	type R/W, o	offset 0x408	B, reset 0x0	0000.0000 (:	see page 2	66)						IS			
SPIOIBE,	type R/W, o	offset 0x408	3, reset 0x0	)000.0000 (:	see page 2	66)									
												IS BE			
				0000.0000 (s											
											II	BE			
GPIOIEV, 1	type R/W, o	offset 0x400	C, reset 0x0	0000.0000 (	see page 2	67)					II				
GPIOIEV, 1	type R/W, o	offset 0x400	C, reset 0x0		see page 2	67)					II	BE			
GPIOIEV, 1	type R/W, o	offset 0x400	C, reset 0x0	0000.0000 (	see page 2	67)					II	BE			
GPIOIEV, 1	type R/W, o	offset 0x40C	C, reset 0x0	0000.0000 (	see page 2	67) 8)					II	BE EV			
GPIOIEV, 1	type R/W, o	offset 0x40C	C, reset 0x0	0000.0000 (s	see page 2	67) 8)					II	BE EV			
GPIOIEV, 1	type R/W, o	offset 0x40C	C, reset 0x0	0000.0000 (s	see page 2	67) 8)					11	BE EV			
GPIOIEV, 1 GPIOIM, 13 GPIORIS,	type R/W, c	offset 0x40C	reset 0x00	0000.0000 (s	see page 26	8) 9)					11	BE EV			
GPIOIEV, 1 GPIOIM, ty	type R/W, c	offset 0x40C	reset 0x00	000.0000 (st	see page 26	8) 9)					11	BE EV			
GPIOIEV, 1	type R/W, c	offset 0x40C	reset 0x00	000.0000 (st	see page 26	8) 9)					III III	BE EV			
SPIOIEV, 1 SPIOIM, t) SPIORIS,	type R/W, of	iffset 0x40C	reset 0x00	000.0000 (st	see page 26 ee page 26 eee page 26 eee page 27	9)					III III	BE EV			
GPIOIEV, ( GPIOIM, t) GPIORIS,	type R/W, of	iffset 0x40C	reset 0x00	0000.0000 (s	see page 26 ee page 26 eee page 26 eee page 27	9)					III III	BE EV			

31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16
15	14	13	12	11	10	9	8	7	6	5	4	3	2	1	0
GPIOAFS	EL, type R/	W, offset 0	x420, rese	t - (see pag	e 272)							ļ			
	, ,,,,,	,	1		,										
											AF	SEL			
CDIODD2	R, type R/W	/ offeet fly	500 reset		E (see pag	0 274)									
OI IODINZ	it, type to the	i, onset ox	.500, 16361		(see pag	C 214)									
											Di	7) (0			
											DI	RV2			
GPIODR4	R, type R/W	/, offset 0x	504, reset	0x0000.000	0 (see pag	e 275)		1							
											DI	RV4			
GPIODR8	R, type R/W	, offset 0x	508, reset	0x0000.000	0 (see pag	e 276)									
											DI	RV8			
GPIOODF	R, type R/W,	offset 0x5	OC, reset 0	x0000.000	(see page	277)									
											0	DE .			
GPIOPLIP	R, type R/W,	Offset Nys	10 reset	(see nage 3	78)			1							
JI IJFUR	, type tow,	CHOOL UXD	15, 16561 -	(See page 2	., 0)										
												IIE			
											Р	UE			
GPIOPDR	R, type R/W,	offset 0x5	14, reset 0	x0000.0000	(see page	279)		1							
											P	DE			
GPIOSLR	type R/W,	offset 0x5	18, reset 0	k0000.0000	(see page	280)									
											S	RL			
GPIODEN	I, type R/W,	offset 0x5	1C, reset -	(see page 2	281)			1							
			,		,										
											D	I EN			
GRIOL OC	K, type R/V	V offeet Ox	(520 rosot	0~0000 000	11 (see pag	0 282)		1							
GFIOLOG	in, type in	v, Oliset Uz	1320, 16361	0.0000.000	i (see pag	6 202)	1.0	2014							
								OCK							
							LC	OCK							
GPIOCR,	type -, offse	et 0x524, r	eset - (see	page 283)				1							
											(	CR			
<b>GPIOPeri</b>	phID4, type	RO, offse	t 0xFD0, re	set 0x0000	.0000 (see	page 285)									
											Р	ID4			
GPIOPeri	phID5, type	RO, offse	t 0xFD4, re	set 0x0000	.0000 (see	page 286)									
					,										
											P	I ID5			
GPIOPori	phID6, type	RO offer	t OxEDS ro	Set Oynnon	0000 (see	nage 287)		1			•	-			
JE IOPEN	pilipo, type	ico, onse	t JAI DO, FE	Jet OXUUUU	.5000 (566	paye 201)									
											Р	ID6			
GPIOPeri	phID7, type	RO, offse	t 0xFDC, re	set 0x0000	.0000 (see	page 288)									
											Р	ID7			
GPIOPeri	phID0, type	RO, offse	t 0xFE0, re	set 0x0000	.0061 (see	page 289)									
											Р	I ID0			
GPIOPori	phID1, type	RO offer	t OxFE4 ro	set Oynnon	0000 (see	nage 200)		1							
JE IOPEN	pilio i, type	ico, onse	. JAI E4, FB	Jet OXOOOO	.5000 (566	paye 280)									
											_	10.4			
											Р	ID1			

24	20	20	20	07	26	25	24	22	22	24	20	10	10	17	16
31 15	30 14	29 13	28 12	27 11	26 10	25 9	24 8	23 7	6	21 5	20	19	18	17	16 0
			0xFE8, res				0		0	3	7			'	0
01 101 011	<b>52</b> , type	110, 011001	OXI 20, 100		0010 (000)	page 201)									
											PI	D2			
GPIOPerin	hID3, type	RO. offset	0xFEC, res	set 0x0000	.0001 (see	page 292)		l							
		, , , , , ,													
											PI	D3			
GPIOPCell	IID0. type F	RO. offset 0	xFF0, rese	t 0x0000.0	00D (see p	age 293)		l							
	., ., .	,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,	.,		(444)	1 1 1 1									
											CI	D0			
GPIOPCell	IID1, type F	RO, offset 0	xFF4, rese	t 0x0000.0	0F0 (see pa	age 294)		l							
		<i>,</i>	,			,									
											CI	D1			
GPIOPCell	IID2, type F	RO, offset 0	xFF8, rese	t 0x0000.0	005 (see pa	age 295)									
											CI	D2			
GPIOPCell	IID3, type F	RO, offset 0	xFFC, rese	et 0x0000.0	00B1 (see p	age 296)									
											CI	D3			
Timer1 ba	ase: 0x400 ase: 0x400	03.1000													
	ase: 0x400					200)									
GPIMCFG	i, type R/W	, offset uxu	00, reset 0:	X0000.000	u (see page	309)		1				1			
														ODTMOS	
ODTME	ID 4 D4	N - 55 4 O-	-004	00000	00 /	040)								GPTMCFG	
GPIMIAM	IR, type R/\	N, offset ux	(004, reset	0x0000.00	uu (see pag	ge 310)		I				I			
												TAAMS	TACMR	TΛ	MR
COTMTRM	IP type P/	N offeet Ox	k008, reset	0×0000 00	IOO (see pag	70 312)						IAAWO	IAOWIN	IA.	IVIIX
GFTWITDIV	ik, type k/	v, onset o	kooo, reset	0.0000.00	(see pag	Je 312)									
												TBAMS	TBCMR	TR	MR
GPTMCTI	type P/W	offeet 0v0	OC, reset 0:	×0000 000	n (see nage	314)						1 D/ WIO	TBOWN	10	
OI TIMOTE	, type tow,	Oliget Oxo	00, 16361 0		(see page	. 314)									
	TBPWML	TBOTE		TRE	VENT	TBSTALL	TBEN		TAPWML	TAOTE	RTCEN	TAF	VENT	TASTALL	TAEN
			18, reset 0x				TELIV		17 ti VVIVIL	MOTE	TOLIT	1712		I/ (O I/ KEE	171214
OI TIMINITY,	, type lutt,	Oliset oxo	10, 16361 02		(see page	317)									
					CBEIM	СВМІМ	TBTOIM					RTCIM	CAEIM	CAMIM	TATOIM
GPTMRIS	tyne RO o	offset OxO1	C, reset 0x0	0000 0000								1110	07121111	07 1111111	., ., .
C	.,po 100, 0		-, 1000t UA		,see page (	,									
					CBERIS	CBMRIS	TBTORIS					RTCRIS	CAERIS	CAMRIS	TATORIS
GPTMMIS	type RO.	offset 0×02	0, reset 0x(	0000.0000								1 5	_ =: :=: ::0		
0	typo ito, t	J.1301 0X02	o, reset ext		(occ page t	1									
					CBEMIS	CBMMIS	TBTOMIS					RTCMIS	CAEMIS	CAMMIS	TATOMIS
GPTMICE	type W1C	offset 0×0	24, reset 0:	x0000.000								1 33	_ =: :=:::::3		
	. ,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,		.,		, , so page	,									
					CBECINT	CBMCINT	TBTOCINT					RTCCINT	CAECINT	CAMCINT	TATOCINT
GPTMTAII	R. type R/	N. offset 0:	(028, reset	0xFFFF.FF								1			
	, ., ,, , , , , , , , , , , , , , , , ,	, =:::00: 07	,		. (300 po	J/	TAII	LRH							
								LRL							
GPTMTBIL	R, type R/	W, offset 0:	x02C, reset	0x0000.F	FFF (see na	age 324)									
	. ,,		, 117		( pc	,									
							TBI	LRL							
							101								

												T			
31 15	30 14	29 13	28 12	27 11	26 10	25 9	24 8	23 7	22 6	21 5	20	19	18	17	16 0
			fset 0x030,						0	э	4	3		<u> </u>	
GPTWITAN	іАТСПК, іў	pe K/vv, oi	iset uxusu,	reset uxri	FFF.FFFF (S	see page 32		MRH							
								MRL							
GPTMTRM	IATCHR tv	ne R/W of	fset 0x034,	reset 0x00	OOD FFFF (s	ee nage 32		WII KE							
0	, . <b>,</b>	po, c.				page oz									
							TB	l MRL							
GPTMTAP	R, type R/V	V, offset 0x	c038, reset	0x0000.000	00 (see pag	e 327)									
	7 3.	<u>,                                     </u>			\	,									
											TA	PSR			
GPTMTBP	R, type R/V	V, offset 0	x03C, reset	0x0000.00	00 (see pag	je 328)									
											ТВ	PSR			
GPTMTAP	MR, type R	/W, offset	0x040, rese	et 0x0000.0	000 (see pa	age 329)									
											TAF	PSMR			
GPTMTBP	MR, type R	/W, offset	0x044, rese	et 0x0000.0	0000 (see pa	age 330)									
											TBF	PSMR			
GPTMTAR	, type RO,	offset 0x04	48, reset 0x	FFFF.FFFF	(see page	331)									
								ARH							
							TA	ARL							
GPTMTBR	t, type RO,	offset 0x0	4C, reset 0x	(0000.FFFI	F (see page	332)		1							
								l no							
							115	BRL							
	og Time														
	000.0000		000 40		<b></b> (	- 007)									
WDILOAD	), type R/W	, offset Ux	000, reset 0	XFFFF.FFF	-F (see pag	e 337)	WD	Flood							
								ΓLoad ΓLoad							
WDTVALII	IE type PO	offeet Ov	004, reset 0	\~EEEE EE	EE (see pag	0 338)	WD	LUAU							
WDIVALO	L, type NO	, onset ox	004, 16561 (	,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,	i (see pag	e 330)	WDI	Value							
								Value							
WDTCTL. 1	type R/W. o	offset 0x00	8, reset 0x0	0000.0000	(see page 3	39)									
,	.,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,				( p-g										
														RESEN	INTEN
WDTICR, t	type WO, o	ffset 0x000	C, reset - (s	L ee page 34	0)										
							WD	ΓIntClr							
							WD	ΓIntClr							
WDTRIS, t	ype RO, of	fset 0x010	, reset 0x00	000.0000 (s	see page 34	1)									
															WDTRIS
WDTMIS, t	type RO, of	fset 0x014	, reset 0x00	000.0000 (s	see page 34	2)									
															WDTMIS
WDTTEST,	, type R/W,	offset 0x4	18, reset 0	k0000.0000	(see page	343)									
							STALL								
WDTLOCK	K, type R/W	, offset 0x	C00, reset (	0x0000.000	00 (see page	e 344)									
								TLock							
							WD.	TLock							
WDTPerip	hID4, type	RO, offset	0xFD0, res	et 0x0000.	0000 (see p	age 345)									
											P	ID4			

31	20	20	20	27	26	25	24	23	22	24	20	10	10	17	16
15	30 14	29 13	28 12	27 11	10	25 9	24 8	7	22 6	21 5	20 4	19	18	17	16 0
			0xFD4, res				0		0	3	4	] 3		'	U
WD I Felip	ilibo, type i	NO, Uliset	UXI D4, 165	et uxuuuu.t	ooo (see p	age 340)									
											DI	  D5			
WDTBorin	hIDE tuno I	BO officet	0xFD8, res	ot 0×0000 (	1000 (aaa a	247)									
WDIFEIIP	ilibo, type i	NO, Oliset	UXI DO, IES		ooo (see p	age 347)									
											PI	  D6			
WDTBorin	hID7 tuna I	BO officet	0xFDC, res	at 0×0000	0000 (000 n	249)									
WDIFERIP	IIID7, type i	KO, Oliset	UXFDC, 168	et uxuuuu.	ooo (see p	aye 346)									
											DI	  D7			
WDTDarin	hIDO tura I	DO -#	0,4550 400	-4 0-0000 (	00F (acc a	240)		<u> </u>			- FI	וטו			
WDIPenp	nibu, type i	KO, onset	0xFE0, res	et uxuuuu.t	oos (see p	age 349)						1			
											DI	D0			
WDTDarin	hID4 time I	DO -#4	04554 ***	-4 0-0000 (	040 /000 0	250)						100			
WDTPerip	nio i, type i	KO, onset	0xFE4, res	et uxuuuu.t	oro (see p	age 350)									
											DI	D1			
MDTD!	LIDO torre I	DO -#4	0550	-4.00000	040 (	054)					PI	וטו			
WD I Perip	וווט∠, type I	KU, OTTSET	0xFE8, res	et UXUUUU.(	o o (see p	age 351)									
											DI	 			
WDTD:='	hina time	DO 4#= 1	0.4550 =	-4 0×0000	2004 /	250)					PI	D2			
WDIPerip	niD3, type i	RO, offset	0xFEC, res	et uxuuuu.	Juu1 (see p	age 352)									
											DI	 			
					/						PI	ID3			
WDTPCell	ID0, type R	O, offset 0	xFF0, rese	t 0x0000.00	OD (see pa	ge 353)						I			
											CI	ID0			
WDTPCell	ID1, type R	O, offset 0	xFF4, rese	t 0x0000.00	F0 (see pa	ge 354)		1				1			
											CI	ID1			
WDTPCell	ID2, type R	O, offset 0	)xFF8, rese	t 0x0000.00	<b>05</b> (see pag	ge 355)		ı							
											CI	ID2			
WDTPCell	ID3, type R	O, offset 0	xFFC, rese	t 0x0000.00	)B1 (see pa	ge 356)		ı							
											_				
											CI	ID3			
Analog- Base 0x4	_	al Conv	erter (AD	)C)											
ADCACTS	S, type R/W	V, offset 0	x000, reset	0x0000.000	0 (see page	e 367)									
												ASEN3	ASEN2	ASEN1	ASEN0
ADCRIS, ty	ype RO, off	set 0x004	, reset 0x00	000.0000 (se	ee page 368	3)							1		-
												INR3	INR2	INR1	INR0
ADCIM, ty	pe R/W, offs	set 0x008,	reset 0x00	00.0000 (se	e page 369	)									
		, ,													
												MASK3	MASK2	MASK1	MASK0
ADCISC, to	ype R/W1C	, offset 0x	00C, reset (	0x0000.000	0 (see page	370)		I.				1			
					3										
												IN3	IN2	IN1	IN0
ADCOSTA	T, type R/W	1C, offset	0x010, res	et 0x0000.0	000 (see na	age 371)						1	1		
	, ,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,	,	,		, (250 pi	J · · /									
												OV3	OV2	OV1	OV0
ADCEMIY	type P/M	Offset No	014, reset 0	×0000 0000	(see nage	372)						1 2,0			3,0
ADOLINIOA	, type raw,	JIIJEL UX	<del>. ,</del> . e s e i 0		, (see page	J12)									
	EM	13			EM	12			-	M1			-	ИO	
	EIV	10			Er	114			E	vi i			E	VIO	

31	30	29	20	27	26	25	24	23	22	21	20	19	10	17	16
15	14	13	28 12	11	10	25 9	8	7	22 6	21 5	20 4	3	18 2	17	0
	AT, type R/W			L											
												UV3	UV2	UV1	UV0
ADCSSPI	RI, type R/W	, offset 0x	020, reset (	x0000.321	0 (see pag	e 376)									
		S	S3			S	S2			S	S1			S	S0
ADCPSSI	l, type WO,	offset 0x02	28, reset - (s	see page 37	<b>'</b> 8)										
												SS3	SS2	SS1	SS0
ADCSAC,	, type R/W,	offset 0x03	0, reset 0x	0000.0000	(see page	379)									
														AVG	
ADCSSM	UX0, type R	/W, offset		et 0x0000.0	000 (see p	age 380)									
			MUX7				MUX6				MUX5				MUX4
ADCCCC.	TIO 500 - 5	\\\\ cfc - 4.5	MUX3	. 020000 00	00 /22- :	202)	MUX2				MUX1				MUX0
	TL0, type R					-	De	TOF	ICE	ENDE	DE	TC4	IF4	END4	D4
TS7	IE7	END7 END3	D7 D3	TS6 TS2	IE6	END6 END2	D6 D2	TS5 TS1	IE5 IE1	END5 END1	D5 D1	TS4 TS0	IE4 IE0	END4 END0	D4 D0
	FO0, type R					LINDZ	DZ	131	IL.	LINDT	ы	130	ILU	LINDO	
ADOUGH	i Ou, type i	o, onser o	7,040,1636	l - (see pag	000)										
										DA	TA				
ADCSSFI	FO1, type R	O. offset 0	)x068. reset	t - (see pag	e 385)										
	, . , , , , ,	,		(											
										D.A	ιΤΑ				
ADCSSFI	FO2, type R	O, offset 0	)x088, reset	t - (see pag	e 385)										
		,			,										
										DA	ιΤΑ				
ADCSSFI	FO3, type R	O, offset 0	x0A8, rese	t - (see pag	e 385)										
										DA	TΑ				
ADCSSF	STAT0, type	RO, offset	0x04C, res	set 0x0000.	0100 (see	page 386)									
			FULL				EMPTY		HF	PTR			TF	PTR	
ADCSSF	STAT1, type	RO, offset	0x06C, res	set 0x0000.	<b>0100</b> (see	page 386)									
			FULL				EMPTY		HF	PTR			TF	PTR	
ADCSSFS	STAT2, type	RO, offset	0x08C, res	et 0x0000.	0100 (see	page 386)									
			FULL				EMPTY		HF	PTR			TF	PTR	
ADCSSFS	STAT3, type	RO, offset	0x0AC, re	set 0x0000.	.0100 (see	page 386)									
			FULL				EMPTY		HF	PTR			TF	PTR	
ADCSSM	UX1, type R	/W, offset	0x060, rese	et 0x0000.0	<b>000</b> (see p	age 387)									
			MUNO				MUNO				MUNZA				MUNIC
4 DOCC! -	1170 ( =	044 - 27	MUX3	4.00000	000 (:	007)	MUX2				MUX1				MUX0
ADCSSM	UX2, type R	/vv, offset	UXU8U, rese	τ UXUOOO.0	uuu (see p	age 387)									
			MUX3				MUX2				MUX1				MUX0
VDC66C.	TI 1 time D	(M. offoot C		1 020000 00	00 (600 70	ngo 389)	IVIUAZ				IVIUXI				IVIUXU
ADCOOC	TL1, type R	vv, onset t	AUG4, rese	. 020000.00	oo (see pa	iye 300)									
TS3	IE3	END3	D3	TS2	IE2	END2	D2	TS1	IE1	END1	D1	TS0	IE0	END0	D0
100	ILU	L14D3	- 55	102	112	LINDZ	D2	101	15-1	ושוים	וט	100	iLU	F14D0	D0

31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16
15	14	13	12	11	10	9	8	7	6	5	4	3	2	1	0
ADCSSC.	TL2, type R	/W, offset 0	)x084, rese	t 0x0000.00	000 (see pa	ge 388)									
TS3	IE3	END3	D3	TS2	IE2	END2	D2	TS1	IE1	END1	D1	TS0	IE0	END0	D0
ADCSSM	UX3, type F	/W, offset	0x0A0, res	et 0x0000.0	<b>000</b> (see p	age 390)									
															MUX0
ADCSSC.	TL3, type R	/W, offset 0	)x0A4, rese	et 0x0000.00	002 (see pa	age 391)									
												TS0	IE0	END0	D0
ADCTML	B, type R/W	, offset 0x1	100, reset 0	x0000.0000	(see page	: 392)									
															LB
Univer	sal Asyn	chronou	ıs Recei	vers/Trai	nsmitte	rs (UAR1	Γs)								
UARTO I	base: 0x40	00.C000													
UARTDR,	, type R/W,	offset 0x00	0, reset 0x	0000.0000 (	see page 4	102)									
				OE	BE	PE	FE				D	ATA			
UARTRSI	R/UARTEC	R, type RO,	offset 0x0	04, reset 0x	(0000.0000	(Reads) (s	ee page 40	4)							
												OE	BE	PE	FE
UARTRSI	R/UARTEC	R, type WO	, offset 0x0	004, reset 0	x0000.000	(Writes) (s	see page 40	04)							
											D	ATA			
UARTFR,	type RO, o	ffset 0x018	, reset 0x0	<b>000.0090</b> (s	ee page 40	06)									
								TXFE	RXFF	TXFF	RXFE	BUSY			
UARTILP	R, type R/W	, offset 0x	020, reset 0	0x0000.0000	(see page	408)									
											ILPI	OVSR			
UARTIBR	RD, type R/V	V, offset 0x	024, reset (	0x0000.000	0 (see pag	e 409)									
							DI\	/INT							
UARTFBI	RD, type R/	N, offset 0	x028, reset	0x0000.000	00 (see pag	je 410)									
												DIVI	RAC		
UARTLC	RH, type R/	N, offset 0	x02C, reset	0x0000.00	00 (see pa	ge 411)		•							
								SPS	WL	EN	FEN	STP2	EPS	PEN	BRK
UARTCTI	L, type R/W	offset 0x0	30, reset 0:	x0000.0300	(see page	413)									
						RXE	TXE	LBE					SIRLP	SIREN	UARTEN
UARTIFL	S, type R/W	offset 0x0	034, reset 0	x0000.0012	(see page	415)									
											RXIFLSEL			TXIFLSEL	
UARTIM,	type R/W, o	ffset 0x038	3, reset 0x0	0000.0000 (5	see page 4	17)									
					OEIM	BEIM	PEIM	FEIM	RTIM	TXIM	RXIM				
UARTRIS	, type RO, o	offset 0x03	C, reset 0x	0000.000F (	(see page 4	119)									
					OERIS	BERIS	PERIS	FERIS	RTRIS	TXRIS	RXRIS				
UARTMIS	S, type RO,	offset 0x04	0, reset 0x	0000.0000 (	see page 4	120)		•							
					OEMIS	BEMIS	PEMIS	FEMIS	RTMIS	TXMIS	RXMIS				

04	20	00	- 00	0.7	00	05	04	1 00	00	04	00	10	40	47	40
31 15	30 14	29 13	28 12	27 11	26 10	25 9	24 8	23 7	22 6	21 5	20	19	18	17	16 0
				L			0		U	3	4	] 3			
UAKTICK,	type witc,	onset uxu	044, reset 0x	1	(see page	421)									
					OEIC	BEIC	PEIC	FEIC	RTIC	TXIC	RXIC				
LIADTDawie	mbID4 from	DO effec	4 0×FD0 ==				FLIC	TEIC	KIIC	TAIC	IXIC				
UAKTPEN	рпір4, туре	e RO, onse	et 0xFD0, re	Set uxuuuu	1.0000 (see	page 423)									
											DI	D4			
IIA DED		DO -#	1 0 FD4		0000 (	404)					PI	D4			
UARTPeri	pnius, type	RU, offse	et 0xFD4, re	set uxuuuu	1.0000 (see	page 424)						1			
											DI	D5			
		DO "				105)					PI	D5			
UARTPerij	pniD6, type	RO, offse	et 0xFD8, re	set uxuuuu	1.0000 (see	page 425)						1			
											- DI	D0			
											PI	D6			
UARTPeri	phID7, type	RO, offse	et 0xFDC, re	et 0x0000	0.0000 (see	page 426)						1			
											PI	D7			
UARTPeri	phID0, type	RO, offse	et 0xFE0, res	set 0x0000	.0011 (see	page 427)									
											PI	D0			
UARTPeri	phID1, type	RO, offse	et 0xFE4, res	set 0x0000	.0000 (see	page 428)		1							
											PI	D1			
UARTPeri	phID2, type	RO, offse	et 0xFE8, res	set 0x0000	.0018 (see	page 429)									
											PI	D2			
UARTPeri	phID3, type	RO, offse	et 0xFEC, re	set 0x0000	0.0001 (see	page 430)									
											PI	D3			
UARTPCe	IIID0, type I	RO, offset	0xFF0, rese	et 0x0000.0	000D (see p	age 431)									
											CI	D0			
UARTPCel	IIID1, type F	RO, offset	0xFF4, rese	et 0x0000.0	<b>00F0</b> (see p	age 432)									
											CI	D1			
UARTPCe	IIID2, type F	RO, offset	0xFF8, rese	et 0x0000.0	0005 (see pa	age 433)									
											CI	D2			
UARTPCe	IIID3, type F	RO, offset	0xFFC, res	et 0x0000.	<b>00B1</b> (see p	page 434)									
											CI	D3			
Synchro	onous S	erial Int	erface (S	SSI)											
-	e: 0x4000														
SSICR0, ty	pe R/W, of	fset 0x000	), reset 0x00	000.0000 (s	ee page 44	8)									
			SC	CR				SPH	SPO	FF	RF		D	SS	
SSICR1, ty	pe R/W, of	fset 0x004	l, reset 0x00	000.0000 (s	ee page 45	(0)							_	_	
												SOD	MS	SSE	LBM
SSIDR, typ	pe R/W, offs	set 0x008,	reset 0x000	00.0000 (se	e page 452	()								-	
							D	ATA							
SSISR, typ	oe RO, offs	et 0x00C, i	reset 0x000	0.0003 (ser	e page 453)	)									
	,	,		, i											
											BSY	RFF	RNE	TNF	TFE

31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16
15	14	13	12	11	10	9	8	7	6	5	4	3	2	1	0
SSICPSR,	, type R/W,	offset 0x0	10, reset 0x	0000.0000	(see page	455)									
											CPS	DVSR			
SSIIM, typ	oe R/W, offs	set 0x014, ı	reset 0x000	0.0000 (see	page 456	)									
												TXIM	RXIM	RTIM	RORIM
SSIRIS, ty	pe RO, off	set 0x018,	reset 0x000	00.0008 (see	e page 458	3)									
				<u> </u>		,									
												TXRIS	RXRIS	RTRIS	RORRIS
SSIMIS to	vne RO off	set 0x01C	reset 0x00	00.0000 (se	e nage 45	9)									
OOMMO, ty	ype ito, on	Jet OXOTO,	16361 0200	1	c page 43	J)									
												TVAUO	DVMIO	DTMIC	DODMIO
												TXMIS	RXMIS	RTMIS	RORMIS
SSIICR, ty	ype W1C, o	ffset 0x020	), reset 0x0	000.0000 (s	ee page 4	60)									
														RTIC	RORIC
SSIPeriph	nID4, type F	RO, offset 0	xFD0, rese	t 0x0000.00	000 (see pa	age 461)									
											Р	ID4			
SSIPeriph	nID5, type F	RO, offset 0	xFD4, rese	t 0x0000.00	000 (see pa	age 462)									
											P	ID5			
SSIPerinh	ID6 type F	20 offset (	YFD8 rese	t 0x0000.00	IOO (see n:	age 463)		1							
oon onpi		lo, onser e	, x, D0, 1000		(occ p	age 400)									
												IDe			
												ID6			
SSIPeriph	1D7, type F	RO, offset 0	DXFDC, rese	et 0x0000.00	<b>000</b> (see p	age 464)		1							
											P	ID7			
SSIPeriph	ID0, type F	RO, offset 0	xFE0, rese	t 0x0000.00	122 (see pa	age 465)									
											Р	ID0			
SSIPeriph	nID1, type F	RO, offset 0	xFE4, rese	t 0x0000.00	00 (see pa	age 466)									
											Р	ID1			
SSIPeriph	nID2, type F	RO, offset 0	xFE8, rese	t 0x0000.00	18 (see pa	age 467)									
											P	I ID2			
SSIPerinh	ID3 tyne F	20 offset (	YFFC rese	t 0x0000.00	<b>101</b> (see n	ane 468)		1							
COII CIIPI	iibo, typo i		JAI 20, 1000		<b>701</b> (000 p	uge 400)									
												ID3			
												103			
SSIPCellI	ບປ, type R0 ⊤	כ, oπset 0x	reset	0x0000.000	u (see pag	ge 469)		1							
											С	ID0			
SSIPCellI	D1, type R0	O, offset 0x	FF4, reset	0x0000.00F	0 (see pag	ge 470)									
											С	ID1			
SSIPCellI	D2, type R0	O, offset 0x	FF8, reset	0x0000.000	5 (see pag	je 471)									
											С	ID2			
SSIPCelli	D3. type R0	O. offset fly	FFC, reset	0x0000.00E	31 (see na	ge 472)		1							
	-, -, po ix	, =	, . 5550		. (300 pa	J <b>-</b> /									
											^	ID3			
								1			C	ID3			

								I							
31 15	30 14	29 13	28 12	27 11	26 10	25 9	24 8	23 7	22 6	21 5	20 4	19 3	18	17	16 0
			12	11	10	9	0		0	3	4			'	0
Etherne	et Contro et MAC 4004.8000	oller													
	MACIACK, t	ype RO, of	fset 0x000	, reset 0x00	000.0000 (F	Reads)									
						,									
									PHYINT	MDINT	RXER	FOV	TXEMP	TXER	RXINT
MACRIS/N	MACIACK, t	ype WO, o	ffset 0x000	, reset 0x0	000.0000 (	Writes)									
									PHYINT	MDINT	RXER	FOV	TXEMP	TXER	RXINT
MACIM, ty	pe R/W, of	set 0x004,	reset 0x00	00.007F											
									PHYINTM	MDINTM	RXERM	FOVM	TXEMPM	TXERM	RXINTM
MACRCTI	L, type R/W	offset 0x0	008, reset 0	x0000.000	8										
											RSTFIFO	BADCRC	PRMS	AMUL	RXEN
MACTCTL	_, type R/W,	offset 0x0	0C, reset 0	x0000.000	0										
											DUPLEX		CRC	PADEN	TXEN
MACDATA	A, type RO,	offset 0x0	10, reset 0x	0000.0000	(Reads)										
								DATA							
							RXI	DATA							
MACDATA	A, type WO,	offset 0x0	10, reset 0:	x0000.0000	(Writes)										
								DATA							
							TXL	DATA							
MACIA0, t	type R/W, o	Hset 0x014										0070			
				OCT4 OCT2							MAC	OCT1			
MACIA1 1	type R/W, o	ffeat 0v019									WAO				
WACIA1,	type Krvv, o	IISEL UXU IC	, reset uxu												
			MAC	I OCT6							MAC	OCT5			
MACTHR	type R/W,	offset 0x01									1417.10				
WAOTIN,	type law,	JIIJEL UXU I	0, 16361 02												
												THR	ESH		
MACMCT	L, type R/W	offset 0x0	)20. reset 0	×0000 000	0										
	_, ,,,,	,			_										
										REGADR				WRITE	START
MACMDV,	type R/W,	offset 0x02	24, reset 0x	0000.0080				1							
											D	IV			
МАСМТХІ	D, type R/W	, offset 0x	D2C, reset (	0x0000.000	10										
							MI	OTX							
MACMRX	D, type R/W	, offset 0x	030, reset (	0x0000.000	0										
							ME	DRX							
MACNP, ty	ype RO, off	set 0x034,	reset 0x00	00.000											
												NI	PR		
MACTR, t	ype R/W, of	fset 0x038	, reset 0x00	000.000											
															NEWTX

31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16
15	14	13	12	11	10	9	8	7	6	5	4	3	2	1	0
	et Contro nagemer														
MR0, type	e R/W, addr	ess 0x00, r	eset 0x310	0											
RESET	LOOPBK	SPEEDSL	ANEGEN	PWRDN	ISO	RANEG	DUPLEX	COLT							
MR1, type	e RO, addre	ss 0x01, re	eset 0x7849	,								•			
	100X_F	100X_H	10T_F	10T_H					MFPS	ANEGC	RFAULT	ANEGA	LINK	JAB	EXTD
MR2, type	e RO, addre	ss 0x02, re	eset 0x000E												
							OUI	[21:6]							
MR3, type	e RO, addre	ss 0x03, re	eset 0x7237	•											
		OUI	I[5:0]					M	1N				F	:N	
	e R/W, addr		eset 0x01E	1											
NP		RF					A3	A2	A1	A0			S		
	e RO, addre		eset 0x0000												
NP	ACK	RF				A[7	7:0]						S		
MR6, type	e RO, addre	ss 0x06, re	eset 0x0000	) 							DEE	LDUDA		DEV	I DANIES:
MD40 to	D04/I-I			40							PDF	LPNPA		PRX	LPANEGA
RPTR	pe R/W, add	ness ux10,	TXHIM	40 SQEI	NL10					APOL	RVSPOL			PCSBP	RXCC
	pe R/W, add	ross Ov11			INL IU					AFOL	KVSFUL			PUSBP	KACC
	RXER IE		PDF_IE		I SCHG IE	REALILT IE	ANEGCOMP_E	JARRER INT	RYFR INT	PRX INT	PDF INT	I PACK INT	I SCHG INT	REALILT INT	ANECCOMP NT
	pe RO, addı				200110_12	TRI MOET_IE	/12000M_E	0.000.1	TOTELL	1100_1111	1 21	LI MOR_IIVI	LOOKIO_IIVI	1471021_111	71233311311
, .,,			ANEGF	DPLX	RATE	RXSD	RX_LOCK								
MR19, typ	pe R/W, add	lress 0x13,													
	XO														
MR23, typ	pe R/W, add	lress 0x17,	reset 0x00	10					-	-	-		-		
									LED	1[3:0]			LED	0[3:0]	
MR24, ty	pe R/W, add	lress 0x18,	reset 0x00	C0											
								PD_MODE	AUTO_SW	MDIX	MDIX_CM		MDI	K_SD	
Analog	Compa	rators													
Base 0x	4003.C000	)													
ACMIS, ty	ype R/W1C,	offset 0x0	00, reset 0x	0000.0000	(see page	526)									
														IN1	IN0
ACRIS, ty	pe RO, offs	set 0x004, r	reset 0x000	<b>0.0000</b> (see	e page 527)										
														IN1	INIO
ACINTEN	I, type R/W,	offset Oxor	08. reset 0×	0000.000	(see page F	528)								IIVI	IN0
. CONTILIV	., ., po 1014,	JIIGGE GAUG	, 1036t UX		(see page (										
														IN1	IN0
ACREFC	TL, type R/V	V, offset 0x	(010, reset	0x0000.000	0 (see page	e 529)									
	.,														
						EN	RNG						VF	EF.	
ACSTAT0	, type RO,	offset 0x02	0, reset 0x0	0000.0000 (	see page 5	30)									
														OVAL	
ACSTAT1	, type RO,	offset 0x04	0, reset 0x0	0000.0000 (	see page 5	30)									
														OVAL	
ACCTL0,	type R/W, o	offset 0x024	4, reset 0x0	0000.0000 (:	see page 53	31)									
				TOTAL		OCD.		TO11/41	-	·FNI	1017/41		EN	OINE (	
				TOEN	ASI	RCP		TSLVAL	l LS	EN	ISLVAL	l IS	EN	CINV	

31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16
15	14	13	12	11	10	9	8	7	6	5	4	3	2	1	0
ACCTL1,	type R/W, o	ffset 0x044	l, reset 0x0	000.0000 (	see page 53	31)									
				TOEN	ASF	RCP		TSLVAL	TS	EN	ISLVAL	IS	EN	CINV	

# **C** Ordering and Contact Information

# C.1 Ordering Information




Table C-1. Part Ordering Information

Orderable Part Number	Description
LM3S6422-IBZ25-A2	Stellaris® LM3S6422 Microcontroller Industrial Temperature 108-ball BGA
LM3S6422-IBZ25-A2T	Stellaris LM3S6422 Microcontroller Industrial Temperature 108-ball BGA Tape-and-reel
LM3S6422-EQC25-A2	Stellaris LM3S6422 Microcontroller Extended Temperature 100-pin LQFP
LM3S6422-EQC25-A2T	Stellaris LM3S6422 Microcontroller Extended Temperature 100-pin LQFP Tape-and-reel
LM3S6422-IQC25-A2	Stellaris LM3S6422 Microcontroller Industrial Temperature 100-pin LQFP
LM3S6422-IQC25-A2T	Stellaris LM3S6422 Microcontroller Industrial Temperature 100-pin LQFP Tape-and-reel

# C.2 Part Markings

The Stellaris microcontrollers are marked with an identifying number. This code contains the following information:

- The first line indicates the part number, for example, LM3S9B90.
- In the second line, the first eight characters indicate the temperature, package, speed, revision, and product status. For example in the figure below, IQC80C0X indicates an Industrial temperature (I), 100-pin LQFP package (QC), 80-MHz (80), revision C0 (C0) device. The letter immediately following the revision indicates product status. An X indicates experimental and requires a waiver; an S indicates the part is fully qualified and released to production.
- The remaining characters contain internal tracking numbers.



### C.3 Kits

The Stellaris Family provides the hardware and software tools that engineers need to begin development quickly.

- Reference Design Kits accelerate product development by providing ready-to-run hardware and comprehensive documentation including hardware design files
- Evaluation Kits provide a low-cost and effective means of evaluating Stellaris microcontrollers before purchase
- Development Kits provide you with all the tools you need to develop and prototype embedded applications right out of the box

See the website at www.ti.com/stellaris for the latest tools available, or ask your distributor.

# C.4 Support Information


For support on Stellaris products, contact the TI Worldwide Product Information Center nearest you: http://www-k.ext.ti.com/sc/technical-support/product-information-centers.htm.

# D Package Information

# D.1 100-Pin LQFP Package

# D.1.1 Package Dimensions

Figure D-1. Stellaris LM3S6422 100-Pin LQFP Package Dimensions



**Note:** The following notes apply to the package drawing.


**1.** All dimensions shown in mm.

- 2. Dimensions shown are nominal with tolerances indicated.
- 3. Foot length 'L' is measured at gage plane 0.25 mm above seating plane.

[	Body +2.00 mm Footprint, 1.4 mm package thickness								
Symbols	Leads	100L							
A	Max.	1.60							
A <sub>1</sub>	-	0.05 Min./0.15 Max.							
A <sub>2</sub>	±0.05	1.40							
D	±0.20	16.00							
D <sub>1</sub>	±0.05	14.00							
E	±0.20	16.00							
E <sub>1</sub>	±0.05	14.00							
L	+0.15/-0.10	0.60							
е	Basic	0.50							
b	+0.05	0.22							
θ	-	0°-7°							
ddd	Max.	0.08							
ccc	Max.	0.08							
JEDEC F	JEDEC Reference Drawing								
Variat	ion Designator	BED							

### D.1.2 Tray Dimensions

Figure D-2. 100-Pin LQFP Tray Dimensions



# D.1.3 Tape and Reel Dimensions

**Note:** In the figure that follows, pin 1 is located in the top right corner of the device.





Figure D-3. 100-Pin LQFP Tape and Reel Dimensions

# D.2 108-Ball BGA Package

# D.2.1 Package Dimensions

Figure D-4. Stellaris LM3S6422 108-Ball BGA Package Dimensions




**Note:** The following notes apply to the package drawing.

- 1. ALL DIMENSIONS ARE IN MILLIMETERS.
- 2. 'e' REPRESENTS THE BASIC SOLDER BALL GRID PITCH.
- 3. 'M' REPRESENTS THE BASIC SOLDER BALL MATRIX SIZE.
  AND SYMBOL 'N' IS THE NUMBER OF BALLS AFTER DEPOPULATING.
- $\triangle$  'b' is measurable at the maximum solder ball diameter after reflow parallel to primary daium  $\boxed{c}$  .
- ⚠ DIMENSION 'ccc' IS MEASURED PARALLEL TO PRIMARY DATUM [].
- PRIMARY DATUM [] AND SEATING PLANE ARE DEFINED BY THE SPHERICAL CROWNS OF THE SOLDER BALLS.
- 7. PACKAGE SURFACE SHALL BE MATTE FINISH CHARMILLES 24 TO 27.
- 8. SUBSTRATE MATERIAL BASE IS BT RESIN.
- 9. THE OVERALL PACKAGE THICKNESS "A" ALREADY CONSIDERS COLLAPSE BALLS
- 10. DIMENSIONING AND TOLERANCING PER ASME Y14.5M 1994.

Symbols	MIN	NOM	MAX
Α	1.22	1.36	1.50
A1	0.29	0.34	0.39
A3	0.65	0.70	0.75
С	0.28	0.32	0.36
D	9.85	10.00	10.15
D1		8.80 BSC	
E	9.85	10.00	10.15
E1		8.80 BSC	
b	0.43	0.48	0.53
bbb		.20	
ddd		.12	
е		0.80 BSC	
f	-	0.60	-
M		12	
n		108	
	REF: C	JEDEC MO-219F	


### D.2.2 Tray Dimensions

Figure D-5. 108-Ball BGA Tray Dimensions



#### **Tape and Reel Dimensions** D.2.3

Figure D-6. 108-Ball BGA Tape and Reel Dimensions



THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO C-PAK PTE.LTD.

#### **IMPORTANT NOTICE**

Texas Instruments Incorporated and its subsidiaries (TI) reserve the right to make corrections, modifications, enhancements, improvements, and other changes to its products and services at any time and to discontinue any product or service without notice. Customers should obtain the latest relevant information before placing orders and should verify that such information is current and complete. All products are sold subject to TI's terms and conditions of sale supplied at the time of order acknowledgment.

TI warrants performance of its hardware products to the specifications applicable at the time of sale in accordance with TI's standard warranty. Testing and other quality control techniques are used to the extent TI deems necessary to support this warranty. Except where mandated by government requirements, testing of all parameters of each product is not necessarily performed.

TI assumes no liability for applications assistance or customer product design. Customers are responsible for their products and applications using TI components. To minimize the risks associated with customer products and applications, customers should provide adequate design and operating safeguards.

TI does not warrant or represent that any license, either express or implied, is granted under any TI patent right, copyright, mask work right, or other TI intellectual property right relating to any combination, machine, or process in which TI products or services are used. Information published by TI regarding third-party products or services does not constitute a license from TI to use such products or services or a warranty or endorsement thereof. Use of such information may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

Reproduction of TI information in TI data books or data sheets is permissible only if reproduction is without alteration and is accompanied by all associated warranties, conditions, limitations, and notices. Reproduction of this information with alteration is an unfair and deceptive business practice. TI is not responsible or liable for such altered documentation. Information of third parties may be subject to additional restrictions.

Resale of TI products or services with statements different from or beyond the parameters stated by TI for that product or service voids all express and any implied warranties for the associated TI product or service and is an unfair and deceptive business practice. TI is not responsible or liable for any such statements.

TI products are not authorized for use in safety-critical applications (such as life support) where a failure of the TI product would reasonably be expected to cause severe personal injury or death, unless officers of the parties have executed an agreement specifically governing such use. Buyers represent that they have all necessary expertise in the safety and regulatory ramifications of their applications, and acknowledge and agree that they are solely responsible for all legal, regulatory and safety-related requirements concerning their products and any use of TI products in such safety-critical applications, notwithstanding any applications-related information or support that may be provided by TI. Further, Buyers must fully indemnify TI and its representatives against any damages arising out of the use of TI products in such safety-critical applications.

TI products are neither designed nor intended for use in military/aerospace applications or environments unless the TI products are specifically designated by TI as military-grade or "enhanced plastic." Only products designated by TI as military-grade meet military specifications. Buyers acknowledge and agree that any such use of TI products which TI has not designated as military-grade is solely at the Buyer's risk, and that they are solely responsible for compliance with all legal and regulatory requirements in connection with such use.

Applications

TI products are neither designed nor intended for use in automotive applications or environments unless the specific TI products are designated by TI as compliant with ISO/TS 16949 requirements. Buyers acknowledge and agree that, if they use any non-designated products in automotive applications, TI will not be responsible for any failure to meet such requirements.

Following are URLs where you can obtain information on other Texas Instruments products and application solutions:

v.ti.com/automotive
v.ti.com/communications
v.ti.com/computers
v.ti.com/consumer-apps
v.ti.com/energy
v.ti.com/industrial
v.ti.com/medical
v.ti.com/security
v.ti.com/space-avionics-defense
v.ti.com/video
v.ti. v.ti. v.ti.

Wireless Connectivity <u>www.ti.com/wirelessconnectivity</u>

OMAP Mobile Processors www.ti.com/omap

**Products** 

TI E2E Community Home Page

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265 Copyright © 2012, Texas Instruments Incorporated

e2e.ti.com