

# THIS SPEC IS OBSOLETE

**Spec No**: 38-07734

# Spec Title: CY22388/CY22389/CY22391, FACTORY PROGRAMMABLE, QUAD PLL CLOCK GENERATOR WITH VCXO

Replaced by: NONE



# Factory Programmable, Quad PLL Clock Generator with VCXO

### Features

- Fully integrated phase-locked loops (PLLs)
- Small quad flat no-leads (QFN) package option
   40% smaller than 20-pin TSSOP
   22% smaller than 16-pin TSSOP
- Selectable output frequency
- Programmable output frequencies
- Output frequency range:
   1 MHz to 166 MHz
- Input frequency range:
   Crystal: 10 MHz to 30 MHz
   External reference: 1 MHz to 100 MHz
- Analog voltage-control crystal oscillator (VCXO)
- 16-/20-pin TSSOP and 32-pin QFN packages
- 3.3-V operation with 2.5-V output buffer option


# Logic Block Diagram

### **Benefits**

- Meets most digital set top box, DVD recorder, and DTV application requirements
- Multiple high-performance PLLs allow synthesis of unrelated frequencies
- Integration eliminates the need for external loop filter components
- Meets critical timing requirements in complex system designs
- Enables application compatibility
- Complete VCXO solution with ±120 ppm (typical pull range)

### **Functional Description**

For a complete list of related documentation, click here.



CY22391 only)

Cypress Semiconductor Corporation Document Number: 38-07734 Rev. \*L

٠



## Contents


Pinouts	3
Pin Definitions	4
General Description	
Factory-Programmable CY22388/89/91	5
PLLs	5
Frequency Select Pin Operation	
Analog VCXO	
VCXO Profile	
Absolute Maximum Conditions	
Pullable Crystal Specifications	7
Operating Conditions	
DC Parameters	8
AC Parameters	
Test and Measurement	
Voltage and Timing Definitions	

Ordering Information	11
Possible Configurations	11
Ordering Code Definitions	11
Package Drawing and Dimensions	12
Acronyms	14
Document Conventions	14
Units of Measure	14
Document History Page	15
Document mistory rage	13
Sales, Solutions, and Legal Information	
	17
Sales, Solutions, and Legal Information	<b> 17</b> 17
Sales, Solutions, and Legal Information Worldwide Sales and Design Support	<b> 17</b> 17 17
Sales, Solutions, and Legal Information Worldwide Sales and Design Support Products	<b> 17</b> 17 17 17




### Pinouts


### Figure 1. 16-pin TSSOP pinout



### Figure 2. 20-pin TSSOP pinout









# **Pin Definitions**

Pin Name Pin Number		Pin Description		
Fill Name	16-pin TSSOP	20-pin TSSOP	32-pin QFN	Fill Description
XIN	1	1	30	Crystal input or reference clock input
XOUT	16	20	27	Crystal output (No connect if external clock is used)
CLKA	7	9	11	Clock output
CLKB	8	8	10	Clock output
CLKC	9	10	14	Clock output
CLKD	10	7	9	Clock output
CLKE	11	11	15	Clock output
CLKF	n/a	12	17	Clock output
CLKG	n/a	13	18	Clock output
CLKH	n/a	4	8	Clock output
FS0	2	2	31	Frequency select 0
FS1	3	3	32	Frequency select 1
FS2	14	17	23	Frequency select 2
OE/PD#	n/a	18	24	Programmable control pin: Output enable (active-high) or power-down (active-low)
VIN	4	16	1	Analog control input for VCXO
VDD	5, 13, 15	5, 15, 1 <mark>9</mark>	2, 3, 16, 21, 22,	Voltage supply
			25, 26	
VSS	6, 12	6, 14	4, 5, 6, 7, 19, 20	Ground
NC	N/A	N/A	12, 13, 28, 29	No connect.



### **General Description**

The CY22388 family of devices has an analog VCXO, four PLLs, up to eight clock outputs and frequency selection capabilities. The frequency selects do not modify any PLL frequency. Instead they allow the user to choose among eight different output divider selections depending on the clock and package configuration. This is illustrated in Frequency Select Pin Operation.

There is one programmable OE/PD#. The OE/PD# pin can be programmed as either an output enable pin or a power-down pin. The OE function can be programmed to disable a selected set of outputs when low, leaving the remaining outputs running. Full-chip power-down disables all outputs and the PLLs and most of the active circuitry when low.

#### Factory-Programmable CY22388/89/91

Factory programming is available for high- or low-volume manufacturing by Cypress. All requests must be submitted to the local Cypress field application engineer (FAE) or sales representative. After the request is processed, you receive a new part number, samples, and datasheet with the programmed values. This part number is used for additional sample requests and production orders.

### PLLs

The advantage of having four PLLs is that a single device can generate up to four independent frequencies from a single crystal. Generally a design may require up to four oscillators to accomplish what could be done with a single CY22388.

Each PLL is independent and can be configured to generate a voltage-controlled oscillator (VCO) frequency between 62.5 MHz and 250 MHz. Each PLL can then, in turn, be divided down with post dividers to generate the clock output frequency of the user's choice. The output divider allows each clock output to be divided by 1, 2, 3, 4, 5, 6, 8, 9, 10, 12 or 15. The PLL maximum is reduced to 166 MHz in 'divide by 1' mode due to output buffer limitations.

Outputs that allow frequency switching perform a glitch-free transition. A glitch is defined as a high- or low-time shorter than half the smaller of the two periods being switched between. Extended low time (even many cycles in duration) is acceptable.

Selected clock outputs are capable of being powered off a separate 2.5-V supply. This allows for driving lower voltage swing inputs. The CY22388/89/91 device still requires 3.3 V to power the oscillator and all other internal PLL circuitry. For the 2.5-V output option, refer to the CY22388 application note. Selected clocks and pinout diagrams are explained in this application note.

Clock D can obtain its output from either the reference source or PLL1/N1 with N1 being defined as the output divider for PLL1. Clock H is defined as a copy of clock D. Clock D is only available from PLL1/N1 on the 16-pin package.

For CY22388, CLKB and CLKC have related frequencies. For CY22389 and CY22391, CLKD and CLKF have related frequencies, CLKA and CLKB have related frequencies, and CLKC and CLKE have related frequencies. Related frequencies come from the same PLL but can have different divider values.


To minimize parts per million (PPM) error on the clock outputs, you must choose a crystal reference frequency that is a common multiple of the desired PLL frequencies. While this is the ideal situation, this is not always the case and the PLLs have high-resolution counters internally to help minimize frequency deviation from the desired frequency.

PLL VCO frequencies are generated by the following equation:  $F_{VCO} = F_{RFF} \times (P / Q)$ 

where  $F_{REF}$  is the reference input frequency, P is the PLL feedback divider, and Q is the reference input divider.

A PLL is a feedback system where the VCO frequency divided by P and reference frequency divided by Q are constantly being compared and the VCO frequency is adjusted to achieve a locked state. Figure 4 is a simplified drawing of a PLL.

#### Figure 4. PLL system



### **Frequency Select Pin Operation**

#### Table 1. CY22388 16-pin TSSOP

Output Signal	Frequency Selection Lines
CLK A	FS2, FS1, FS0
CLK B	FS1, FS0
CLK C & CLK D	SO
CLK E	FIXED

#### Table 2. CY22389 20-pin TSSOP

Output Signal	Frequency Selection Lines
CLKA	FS2, FS1, FS0
CLK B & CLK C	FS1, FS0
CLK D, CLK E, & CLK F	FS0
CLK G	FIXED
CLK H	COPY OF CLK D

#### Table 3. CY22391 32-pin QFN

Output Signal	Frequency Selection Lines
CLK A	FS2, FS1, FS0
CLK B & CLK C	FS1, FS0
CLK D, CLK E, & CLK F	FS0
CLK G	FIXED
CLK H	COPY OF CLK D



# Analog VCXO

There are three programmable reference operating modes for the CY22388, CY22389, and CY22391 family of devices. The first mode uses an external pullable crystal and incorporates an internal analog VCXO.

The second mode configures the internal crystal oscillator to accept an external driven reference source from 1 to 100 MHz. The input capacitance on the XIN PIN when driven in this mode is 15 pF.

The third mode disables the VCXO input control and sets the internal oscillator to a fixed frequency operation. The load capacitance seen by the external crystal when connected to PINS XIN and XOUT is equal to 12 pF.


One of the key components in the CY22388, CY22389, and CY22391 family of devices is the analog VCXO. The VCXO is used to 'pull' the reference crystal higher or lower to lock the system frequency to an external source. This is ideal for applications where the output frequency needs to track along with an external reference frequency that is constantly shifting.

The VCXO is completely analog, so there is infinite resolution on the VCXO pull curve. The analog to digital converter steps that are normally associated with a digital VCXO input is not present in this device. A special pullable crystal must be used in order to have adequate VCXO pull range. Pullable crystal specifications are included in this datasheet.

## VCXO Profile

Figure 5 shows an example of what a VCXO profile looks like. The analog voltage input is on the X-axis and the PPM range is on the Y-axis. An increase in the VCXO input voltage results in a corresponding increase in the output frequency. This has the effect of moving the PPM from a negative to positive offset.

#### Figure 5. VCXO Profile





### **Absolute Maximum Conditions**

Parameter	Description	Condition	Min	Max	Unit
V <sub>DD</sub> /AV <sub>DD</sub> /V <sub>DDL</sub>	Core supply voltage		-0.5	4.6	V
V <sub>IN</sub>	Input voltage	Relative to V <sub>SS</sub>	-0.5	V <sub>DD</sub> + 0.5	VDC
Τ <sub>S</sub>	Temperature, Storage	Non-Functional	-65	125	°C
ESD <sub>HBM</sub>	Electrostatic disch <mark>arge</mark> (ESD) protection (human body model)	MIL-STD-883, Method 3015	2000	_	V
UL-94	Flammability rating	V-0 at 1/8 in.	-	10	ppm
MSL	Moisture sensitivity level	All packages	;	3	-

# Pullable Crystal Specifications

Parameter <sup>[1, 2]</sup>	Description	Comments	Min	Тур	Max	Unit
F <sub>NOM</sub>	13.5-MHz and 27-MHz crystal AT-Cut	Parallel resonance, fundamental mode		See Note 2		
C <sub>LNOM</sub>	Nominal load capacitance	Order crystal at one specific C <sub>LNOM</sub> 0 ppm	11.4	12	12.6	pF
R <sub>1</sub>	Equivalent series resistance (ESR)	Fundamental mode (CL = Series)	-	-	40	Ω
DL	Crystal drive level	Nominal V <sub>DD</sub> at 25 °C over ±120 ppm pull range	_	-	300	μW
C <sub>0</sub> <sup>[3]</sup>	Crystal shunt capacitance		1.5	3	4.0	pF
C <sub>1</sub> <sup>[3]</sup>	Crystal motional capacitance		12	14	16.8	fF
F <sub>3SEPHI</sub> <sup>[2]</sup>	Third overtone separation from 3 × F <sub>NOM</sub>	Mechanical third (high side of $3 \times F_{NOM}$ )	240	-	_	ppm
F <sub>3SEPLO</sub> <sup>[2]</sup>	Third overtone separation from $3 \times F_{NOM}$	Mechanical third (low side of 3 × F <sub>NOM</sub> )	-	-	-120	ppm

# **Operating Conditions**

Parameter	Description	Min	Тур	Max	Unit
V <sub>DD</sub> /AV <sub>DD</sub> /V <sub>DDL</sub>	Operating voltage	3.0	3.3	3.6	V
T <sub>A</sub>	Ambient temperature	-10	-	70	°C
C <sub>LOAD</sub>	Maximum load capacitance	-	-	15	pF
t <sub>PU</sub>	Power-up time for all $V_{\text{DD}}\text{s}$ reach minimum specified voltage (power ramps must be monotonic)	0.05	-	500	ms

#### Notes

- Device operates to the following specs, which are guaranteed by design.
   Refer to online software for a list of approved crystal specifications.
   Increased tolerance available from pull range less than ±120 ppm.



## **DC Parameters**

Parameter <sup>[4]</sup>	Description	Conditions	Min	Тур	Max	Unit
I <sub>OH</sub> <sup>[5]</sup>	Output high current	V <sub>OH</sub> = V <sub>DD</sub> – 0.5, V <sub>DD</sub> = 3.3 V	12	_	_	mA
I <sub>OL</sub> <sup>[5]</sup>	Output low current	V <sub>OL</sub> = 0.5, V <sub>DD</sub> = 3.3 V	12	_	_	mA
IIH	Input high current	V <sub>IH</sub> = V <sub>DD</sub> , excluding Vin, Xin	-	5	10	μA
IIL	Input low current	V <sub>IL</sub> = 0 V, excluding Vin, Xin	-	5	10	μA
V <sub>IH</sub>	Input high voltage	FS0/1/2 OE input CMOS levels	$0.7 \times A_{VDD}$	-	-	V
V <sub>IL</sub>	Input low voltage	FS0/1/2 OE input CMOS levels	-	-	$0.3 \times A_{VDD}$	V
V <sub>VCXO</sub>	VIN input range	Internal setting in VCXO are XOB/A = 110, Offset = 1110, Gain = 101	0	_	A <sub>VDD</sub>	V
C <sub>IN</sub>	Input capacitance	FS0/1/2 and OE pins only	-	_	7	pF
I <sub>VDD</sub>	Supply current	V <sub>DD</sub> /AV <sub>DD</sub> /V <sub>DDL</sub> current	-	60	-	mA
C <sub>INXIN</sub>	Input capacitance at XIN	VCXO disabled external reference	-	15	-	pF
C <sub>INXTAL</sub>	Input capacitance at crystal	VCXO disabled fixed frequency oscillator	_	12	_	pF

Notes
4. Parameters are guaranteed by design and characterization. Not 100% tested in production. All parameters specified with fully loaded outputs.
5. Custom drive level is available upon request.




# **AC Parameters**

Parameter <sup>[4]</sup>	Description	Min	Тур	Max	Units	
1/t1	Output frequency	PLL <sub>minmax</sub> /Divider <sub>maximum</sub>	4.2	-	166	MHz
DC1	Output duty cycle (excluding REFOUT)	Duty cycle is defined in Figure 7; $t_2/t_1$ , 50% of $V_{DD}$ External reference duty cycle between 40% and 60% measured at $V_{DD}/2$ (Clock output is $\leq$ 125 MHz)	45	50	55	%
DC2	Output duty cycle	Duty cycle is defined in Figure 7; $t_2/t_1$ , 50% of V <sub>DD</sub> External reference duty cycle between 40% and 60% measured at V <sub>DD</sub> /2 (Clock output is > 125 MHz)	40	50	60	%
DC <sub>REFOUT</sub>	Output duty cycle	Duty cycle is defined in Figure 7; t <sub>2</sub> /t <sub>1</sub> , 50% of V <sub>DD</sub> (XIN Duty Cycle = 45/55%)	40	50	60	%
ER	Rising edge rate	Output clock edge rate. Measured from 20% to 80% of $V_{DD}$ . $C_{LOAD} = 15 \text{ pF. See Figure 8}.$	0.75	1.2	-	V/ns
EF	Falling edge rate	Output clock edge rate. Measured from 80% to 20% of $V_{DD}$ . $C_{LOAD}$ = 15 pF. See Figure 8.	0.75	1.2	-	V/ns
T <sub>9</sub>	Clock jitter	Period jitter	-	±250	-	ps
T <sub>10</sub>	PLL lock time		-	1	5	ms
f <sub>ΔXO</sub>	VCXO crystal pull range	Using non-SMD-49 crystal Nominal crystal frequency input assumed (0 ppm) at 25 °C and 3.3 V	±110	±120	_	ppm
		Using SMD-49 crystal Nominal crystal frequency input assumed (0 ppm) at 25 °C and 3.3 V	±105	±120	_	ppm


# **Test and Measurement**

### Figure 6. Test and Measurement





# Voltage and Timing Definitions





# **Ordering Information**


All product offerings are factory-programmed customer-specific devices with customized part numbers. The Possible Configurations table shows the available device types, but not complete part numbers. Contact your local Cypress FAE or sales representative for more information.

Part Number		t Number Package Type		Production Flow
Pb-free				
CY22388FZXC		ZZ16	16-pin TSSOP	Commercial, 0 °C to +70 °C
CY22388FZXCT		<b>Z</b> Z16	16-pin TSSOP – Tape and Reel	Commercial, 0 °C to +70 °C

### **Possible Configurations**

Part Number <sup>[6]</sup>	Package	Туре	Production Flow
Pb-free			
CY22388ZXC-xxx	ZZ16	16-pin TSSOP	Commercial, 0 °C to +70 °C
CY22388ZXC-xxxT	ZZ16	16 <mark>-pin T</mark> SSOP – Tape and Reel	Commercial, 0 °C to +70 °C
CY22389ZXC-xxx	ZZ20	20-pin TSSOP	Commercial, 0 °C to +70 °C
CY22389ZXC-xxxT	ZZ20	20-pin TSSOP – Tape and Reel	Commercial, 0 °C to +70 °C
CY22391LTXC-xxx	LT32	32-pin QFN (Sawn)	Commercial, 0 °C to +70 °C
CY22391LTXC-xxxT	LT32	32-pin QFN (Sawn) – Tape and Reel	Commercial, 0 °C to +70 °C

### **Ordering Code Definitions**



#### Note

 The CY22388ZXC-xxx, CY22389ZXC-xxx, and CY22391LTXC-xxx are factory-programmed configurations. For more details, contact your local Cypress FAE or sales representative.



### **Package Drawing and Dimensions**

Figure 10. 16-pin TSSOP (4.40 mm Body) Package Outline, 51-85091





Figure 11. 20-pin TSSOP (4.40 mm Body) Package Outline, 51-85118




51-85118 \*E



### Package Drawing and Dimensions (continued)

Figure 12. 32-pin QFN ((5 × 5 × 1.0 mm) 3.5 × 3.5 E-Pad (Sawn)) Package Outline, 001-30999





# Acronyms

Acronym	Description		
ESD	Electrostatic Discharge		
ESR	Equivalent Series Resistance		
FAE	Field Application Engineer		
FS	Frequency Select		
PJ	Period Jitter		
PLL	Phase-Locked Loop		
QFN	Quad Flat No-leads		
TSSOP	Thin Shrunk Small Outline Package		
VCO	Voltage-Controlled Oscillator		
VCXO	Voltage-Controlled Crystal Oscillator		

### **Document Conventions**

### Units of Measure

Symbol	Unit of Measure		
°C	degree Celsius		
fF	femtofarad		
KΩ	kilohm		
MHz	megahertz		
μΑ	microampere		
μF	microfarad		
μs	microsecond		
μW	microwatt		
mA	milliampere		
ms	millisecond		
mV	millivolt		
ns	nanosecond		
Ω	ohm		
PPM	parts per million		
pF	picofarad		
ps	picosecond		
V	volt		
W	watt		



# **Document History Page**

Revision	ECN	Submission Date	Description of Change
**	320458	03/07/2005	New data sheet.
*A	389649	08/02/2005	Updated Pullable Crystal Specifications: Removed typical value of R1 parameter. Changed maximum value of R1 parameter from 50 $\Omega$ to 40 $\Omega$ . Updated details in "Comments" column corresponding to DL parameter. Changed maximum value of DL parameter from 900 $\mu$ W to 300 $\mu$ W. Updated AC Parameters: Changed minimum value of f <sub><math>\Delta</math>XO</sub> parameter from ±120 ppm to ±110 ppm. Changed typical value of f <sub><math>\Delta</math>XO</sub> parameter from blank to ±120 ppm.
*В	523597	11/12/2006	Updated AC Parameters: Updated details in "Conditions" column corresponding to $f_{\Delta XO}$ parameter. Retained existing values for $f_{\Delta XO}$ parameter corresponding to Test Condition "Using non-SMD-49 crystal specified in "CY22388 Application Note, ANC0002". Added values for $f_{\Delta XO}$ parameter corresponding to Test Condition "Using SMD-49 crystal specified in "CY22388 Application Note, ANC0002". Updated to new template.
*C	2632357	01/13/2009	Updated Document Title to read as "CY22388, CY22389, CY22391 Factory Program mable Quad PLL Clock Generator with VCXO". Updated Logic Block Diagram (Clarified that Power Down (PD#) is active-low). Updated Pinouts: Updated Figure 2 (Replaced PD with PD#). Updated Pin Definitions: Replaced PD with PD# Updated details in "Description" column corresponding to OE/PD# pin. Updated DC Parameters: Updated details in "Conditions" column corresponding to V <sub>VCXO</sub> parameter. Updated details in "Conditions" column corresponding to V <sub>VCXO</sub> parameter. Updated Ordering Information: Updated part numbers. Added a column "Package" and added details in that column. Added a Note "Not recommended for new designs. The LY32 QFN package transition to the LT32 QFN." and referred the note in CY22391LFXC-xxx and CY22391LFXC-xxxT. Updated Package Drawing and Dimensions: spec 51-85188 – Changed revision from *A to *B. Updated to new template.
*D	2897246	03/22/2010	Updated Ordering Information: Added description (Regarding Possible Configurations). Updated Possible Configurations: Updated part numbers. Updated Note 6. Removed Note "Not recommended for new designs. The LY32 QFN package transitions to the LT32 QFN.". Updated Package Drawing and Dimensions: 51-85091 – Changed revision from *A to *B. 51-85118 – Changed revision from *A to *B. 001-30999 – Changed revision from *A to *C. Removed spec 51-85188 *B.



# Document History Page (continued)

Revision	ECN	Submission Date	Description of Change	
۴E	3030336	09/14/2010	Fixed various typos across the document. Updated Features: Fixed formatting. Updated Absolute Maximum Conditions: Updated Absolute Maximum Conditions: Updated value of MSL parameter as 3 for all packages. Updated Operating Conditions: Removed "Recommended" from heading. Updated Ordering Information: No change in part numbers. Added Ordering Code Definitions. Updated Package Drawing and Dimensions: spec 51-85091 – Changed revision from *B to *C. spec 51-85118 – Changed revision from *B to *C. Added Acronyms and Units of Measure. Updated to new template.	
*F	3786734	10/29/2012	Updated Pinouts: Updated Figure 3 (Updated caption only). Updated Ordering Information: Updated part numbers (Added two part numbers (CY22388FZXC and CY22388FZXCT)). Updated Package Drawing and Dimensions: spec 51-85091 – Changed revision from *C to *D. spec 51-85118 – Changed revision from *C to *D. spec 001-30999 – Changed revision from *C to *D.	
*G	4142797	10/01/2013	Updated to new template. Completing Sunset Review.	
*H	4576237	11/21/2014	Updated Features: Updated output frequency range as 1 MHz to 166 MHz. Updated Functional Description: Added "For a complete list of related documentation, click here." at the end. Updated Package Drawing and Dimensions: spec 51-85091 – Changed revision from *D to *E. spec 51-85118 – Changed revision from *D to *E.	
*	5475432	10/14/2016	Updated to new template. Completing Sunset Review.	
*J	5995535	12/15/2017	Updated Cypress Logo and Copyright.	
*К	6520812	03/25/2019	Updated Analog VCXO: Updated description. Updated Pullable Crystal Specifications: Updated Note 2. Updated AC Parameters: Updated details in "Conditions" column corresponding to $f_{\Delta XO}$ parameter. Updated to new template.	
*L	6563840	04/13/2020	Obsolete this document, as the Part numbers are in EOL- Obsolete/ Prune state.	



### Sales, Solutions, and Legal Information

### Worldwide Sales and Design Support

Cypress maintains a worldwide network of offices, solution centers, manufacturer's representatives, and distributors. To find the office closest to you, visit us at Cypress Locations.

#### Products

Arm <sup>®</sup> Cortex <sup>®</sup> Microcontrollers		cypress.com/arm
Automotive	<b>cy</b> pres	s.com/automotive
Clocks & Buffers	С	ypress.com/clocks
Interface	сур	ress.com/interface
Internet of Things		cypress.com/iot
Memory	сур	ress.com/memory
Microcontrollers		cypress.com/mcu
PSoC		cypress.com/psoc
Power Management ICs		cypress.com/pmic
Touch Sensing	(	cypress.com/touch
USB Controllers		cypress.com/usb
Wireless Connectivity	сур	ress.com/wireless

### **PSoC<sup>®</sup> Solutions**

PSoC 1 | PSoC 3 | PSoC 4 | PSoC 5LP | PSoC 6 MCU

#### **Cypress Developer Community**

Community | Code Examples | Projects | Video | Blogs | Training | Components

#### **Technical Support**

cypress.com/support

© Cypress Semiconductor Corporation, 2005–2020. This document is the property of Cypress Semiconductor Corporation and its subsidiaries ("Cypress"). This document, including any software or firmware included or referenced in this document ("Software"), is owned by Cypress under the intellectual property laws and treaties of the United States and other countries worldwide. Cypress reserves all rights under such laws and treaties and does not, except as specifically stated in this paragraph, grant any license under its patents, copyrights, trademarks, or other intellectual property rights. If the Software is not accompanied by a license agreement and you do not otherwise have a written agreement with Cypress governing the use of the Software, then Cypress hereby grants you a personal, non-exclusive, nontransferable license (without the right to sublicense) (1) under its copyright rights in the Software (a) for Software provided in source code form, to modify and reproduce the Software solely for use with Cypress hardware products, only internally within your organization, and (b) to distribute the Software in binary code form externally to end users (either directly or indirectly through resellers and distributes), solely for use on Cypress hardware product units, and (2) under those claims of Cypress's patents that are infringed by the Software (as provided by Cypress, unmodified) to make, use, distribute, and import the Software solely for use with Cypress hardware products. Any other use, reproduction, modification, translation, or compilation of the Software is prohibited.

TO THE EXTENT PERMITTED BY APPLICABLE LAW, CYPRESS MAKES NO WARRANTY OF ANY KIND, EXPRESS OR IMPLIED, WITH REGARD TO THIS DOCUMENT OR ANY SOFTWARE OR ACCOMPANYING HARDWARE, INCLUDING, BUT NOT LIMITED TO, THE IMPLIED WARRANTIES OF MERCHANTABILITY AND FITNESS FOR A PARTICULAR PURPOSE. No computing device can be absolutely secure. Therefore, despite security measures implemented in Cypress hardware or software products, Cypress shall have no liability arising out of any security breach, such as unauthorized access to or use of a Cypress product. CYPRESS DOES NOT REPRESENT, WARRANT, OR GUARANTEE THAT CYPRESS PRODUCTS, WILL BE FREE FROM CORRUPTION, ATTACK, VIRUSES, INTERFERENCE, HACKING, DATALOSS OR THEFT, OR OTHER SECURITY INTRUSION (collectively, "Security Breach"). Cypress disclaims any liability relating to any Security Breach, and you shall and hereby do release Cypress from any claim, damage, or other liability arising from any Security Breach. In addition, the products described in these materials may contain design defects or errors known as erata which may cause the product to deviate from published specifications. To the extent permitted by applicable law, Cypress reserves the right to make changes to this document without further notice. Cypress does not assume any liability arising out of the application or use of any product or circuit described in this document. Any information provided in this document, including any sample design information or programming code, is provided only for reference purposes. It is the responsibility of the user of this document to properly design, program, and test the functionality and safety of any application made of this information and any resulting product. "High-Risk Device," means any "critical Component" means any component of a High-Risk Device whose failure to perform can be reasonably expected to cause, directly or indirectly, the failure of the High-Risk Device, or to affect its safety or effectiveness. Cypress is not liable, in whole or in part, and you shall

Cypress, the Cypress logo, Spansion, the Spansion logo, and combinations thereof, WICED, PSoC, CapSense, EZ-USB, F-RAM, and Traveo are trademarks or registered trademarks of Cypress in the United States and other countries. For a more complete list of Cypress trademarks, visit cypress.com. Other names and brands may be claimed as property of their respective owners.