











LM2670

SNVS036K-APRIL 2000-REVISED JUNE 2016

LM2670 SIMPLE SWITCHER® High Efficiency 3-A Step-Down Voltage Regulator With Sync

Features

- Efficiency Up to 94%
- Simple and Easy to Design With (Using Off-the-Shelf External Components)
- 150-mΩ DMOS Output Switch
- 3.3-V, 5-V, 12-V Fixed Output and Adjustable (1.2 V to 37 V) Versions
- 50-µA Standby Current When Switched OFF
- ±2% Maximum Output Tolerance Over Full Line and Load Conditions
- Wide Input Voltage Range: 8 V to 40 V
- External Sync Clock Capability (280 kHz to 400 kHz)
- 260-kHz Fixed Frequency Internal Oscillator
- -40 to 125°C Operating Junction Temperature Range

2 Applications

- Simple-to-Design, High Efficiency (>90%) Step-**Down Switching Regulators**
- Efficient System Preregulator for Linear Voltage Regulators
- **Battery Chargers**
- Communications and Radio Equipment Regulator With Synchronized Clock Frequency

3 Description

The LM2670 series of regulators are monolithic integrated circuits which provide all of the active functions for a step-down (buck) switching regulator capable of driving up to 3-A loads with excellent line and load regulation characteristics. High efficiency (>90%) is obtained through the use of a low ONresistance DMOS power switch. The series consists of fixed output voltages of 3.3-V, 5-V, and 12-V output version.

The SIMPLE SWITCHER® concept provides for a complete design using a minimum number of external components. The switching clock frequency can be provided by an internal fixed frequency oscillator (260 kHz) or from an externally provided clock in the range of 280 kHz to 400 kHz which allows the use of physically smaller sized components. A family of standard inductors for use with the LM2670 are available from several manufacturers to greatly simplify the design process. The external sync clock provides direct and precise control of the output ripple frequency for consistent filtering or frequency spectrum positioning.

The LM2670 series also has built-in thermal shutdown, current limiting and an ON/OFF control input that can power down the regulator to a low 50-µA quiescent current standby condition. The output voltage is ensured to a ±2% tolerance.

Device Information⁽¹⁾

PART NUMBER	PACKAGE	BODY SIZE (NOM)
	TO-263 (7)	10.10 mm × 8.89 mm
LM2670	TO-220 (7)	14.986 mm × 10.16 mm
	VSON (14)	6.00 mm × 5.00 mm

(1) For all available packages, see the orderable addendum at the end of the data sheet.

Typical Application






Table of Contents

1	Features 1	7.4 Device Functional Modes 12
2	Applications 1	8 Application and Implementation 13
3	Description 1	8.1 Application Information
4	Revision History2	8.2 Typical Applications 16
5	Pin Configuration and Functions	9 Power Supply Recommendations 26
6	Specifications4	10 Layout 27
•	6.1 Absolute Maximum Ratings	10.1 Layout Guidelines27
	6.2 ESD Ratings	10.2 Layout Example 28
	6.3 Recommended Operating Conditions	11 Device and Documentation Support 29
	6.4 Thermal Information	11.1 Device Support29
	6.5 Electrical Characteristics – 3.3 V	11.2 Related Documentation
	6.6 Electrical Characteristics – 5 V	11.3 Receiving Notification of Documentation Updates 29
	6.7 Electrical Characteristics – 12 V	11.4 Community Resources29
	6.8 Electrical Characteristics – All Output Voltage	11.5 Trademarks
	Versions 6	11.6 Electrostatic Discharge Caution
	6.9 Typical Characteristics	11.7 Glossary29
7	Detailed Description	12 Mechanical, Packaging, and Orderable
	7.1 Overview	Information 29
	7.2 Functional Block Diagram 10	12.1 DAP (VSON Package)29
	7.3 Feature Description	


4 Revision History


NOTE: Page numbers for previous revisions may differ from page numbers in the current version.

С	Changes from Revision J (April 2013) to Revision K Added ESD Ratings table, Feature Description section, Device Functional Modes, Application and Implementation					
•	Added ESD Ratings table, Feature Description section, Device Functional Modes, Application and Implementation section, Power Supply Recommendations section, Layout section, Device and Documentation Support section, and Mechanical, Packaging, and Orderable Information section.	1				
•	Removed all references to Computer Design Software LM267X Made Simple (Version 6.0)	1				
С	hanges from Revision I (April 2013) to Revision J	Page				




5 Pin Configuration and Functions





NHM Package 14-Pin VSON Top View



Connect DAP to pin 9 on PCB

Pin Functions

PIN				
NAME	TO-263, TO-220	VSON	I/O	DESCRIPTION
Switch output	1	12, 13, 14	0	Source pin of the internal High Side FET. This is a switching node. Attached this pin to an inductor and the cathode of the external diode.
Input	2	2, 3	1	Supply input pin to collector pin of high side FET. Connect to power supply and input bypass capacitors C_{IN} . Path from VIN pin to high frequency bypass C_{IN} and GND must be as short as possible.
CBOOST/CB	3	4	I	Boot-strap capacitor connection for high-side driver. Connect a high-quality, 100-nF capacitor from CB to VSW Pin.
GND	4	9	_	Power ground pins. Connect to system ground. Ground pins of C_{IN} and C_{OUT} . Path to CIN must be as short as possible.
SYNC	5	6	ı	Synchronization pin. Use this pin to synchronize the frequency to an external clock. The external frequency must be higher than the LM2670 internal oscillation frequency.
Feedback/FB	6	7	ı	Feedback sense input pin. Connect to the midpoint of feedback divider to set VOUT for ADJ version or connect this pin directly to the output capacitor for a fixed output version.
ON/OFF	7	8	I	Enable input to the voltage regulator. High = ON and low = OFF. Pull this pin high or float to enable the regulator.
NC	_	1, 5, 10, 11	_	No connect pins

Copyright © 2000–2016, Texas Instruments Incorporated



6 Specifications

6.1 Absolute Maximum Ratings

See (1)(2)

		MIN	MAX	UNIT
Input supply voltage			45	V
Soft-start pin voltage	ltage -0.1 6			V
Switch voltage to ground ⁽³⁾		-1	V _{IN}	V
Boost pin voltage			V _{SW} + 8	
Feedback pin voltage	eedback pin voltage -0.3 14			V
Power dissipation		Interna	lly Limited	
	Wave, 4 s		260	
Soldering temperature	Infrared, 10 s		240	°C
	Vapor phase, 75 s		219	
Storage temperature, T _{stg}	1 1 1 1 1 1 1 1 1 1 1 1 1 1 1 1 1 1 1 1			°C

- (1) Stresses beyond those listed under Absolute Maximum Ratings may cause permanent damage to the device. These are stress ratings only, which do not imply functional operation of the device at these or any other conditions beyond those indicated under Recommended Operating Conditions. Exposure to absolute-maximum-rated conditions for extended periods may affect device reliability.
- (2) If Military/Aerospace specified devices are required, please contact the Texas Instruments Sales Office/Distributors for availability and specifications.
- (3) The absolute maximum specification of the Switch Voltage to Ground applies to DC voltage. An extended negative voltage limit of –10 V applies to a pulse of up to 20 ns, –6 V of 60 ns and –3 V of up to 100 ns.

6.2 ESD Ratings

			VALUE	UNIT
V _(ESD)	Electrostatic discharge	Human-body model (HBM), per ANSI/ESDA/JEDEC JS-001 ⁽¹⁾⁽²⁾	±2000	٧

- (1) JEDEC document JEP155 states that 500-V HBM allows safe manufacturing with a standard ESD control process.
- (2) ESD was applied using the human-body model, a 100-pF capacitor discharged through a 1.5-kΩ resistor into each pin.

6.3 Recommended Operating Conditions

	MIN	MAX	UNIT
Supply voltage	8	40	V
Junction temperature, T _J	-40	125	ŝ



6.4 Thermal Information

				LM2678		
THERMAL METRIC ⁽¹⁾			NDZ (TO-220)	KTW (TO-263)	NHM (VSON)	UNIT
			7 PINS	7 PINS	14 PINS	
		See (2)	65	_	_	
	Junction-to-ambient thermal resistance	See (3)	45	_	_	
		See (4)	_	56	_	
$R_{\theta JA}$		See (5)	_	35	_	°C/W
		See (6)	_	26	_	
		See (7)	_	_	55	
		See (8)	_	_	29	
$R_{\theta JC(top)}$	BJC(top) Junction-to-case (top) thermal resistance		2	2	_	°C/W

- (1) For more information about traditional and new thermal metrics, see the application report, Semiconductor and IC Package Thermal Metrics
- (2) Junction to ambient thermal resistance (no external heat sink) for the 7-lead TO-220 package mounted vertically, with ½ inch leads in a socket, or on a PCB with minimum copper area.
- (3) Junction to ambient thermal resistance (no external heat sink) for the 7-lead TO-220 package mounted vertically, with ½ inch leads soldered to a PCB containing approximately 4 square inches of (1 oz.) copper area surrounding the leads.
- (4) Junction to ambient thermal resistance for the 7-lead DDPAK mounted horizontally against a PCB area of 0.136 square inches (the same size as the DDPAK package) of 1 oz (0.0014 in thick) copper.
- (5) Junction to ambient thermal resistance for the 7-lead DDPAK mounted horizontally against a PCB area of 0.4896 square inches (3.6 times the area of the DDPAK package) of 1 oz (0.0014 in thick) copper.
- (6) Junction to ambient thermal resistance for the 7-lead DDPAK mounted horizontally against a PCB copper area of 1.0064 square inches (7.4 times the area of the DDPAK 3 package) of 1 oz (0.0014 in thick) copper. Additional copper area will reduce thermal resistance further.
- (7) Junction to ambient thermal resistance for the 14-lead VSON mounted on a PCB copper area equal to the die attach paddle.
- (8) Junction to ambient thermal resistance for the 14-lead VSON mounted on a PCB copper area using 12 vias to a second layer of copper equal to die attach paddle. Additional copper area will reduce thermal resistance further. For layout recommendations, see Application Note AN-1187 Leadless Leadfram Package (LLP).

6.5 Electrical Characteristics - 3.3 V

Specifications apply for $T_A = T_J = 25$ °C unless otherwise noted. $R_{ADJ} = 5.6 \text{ k}\Omega$.

	PARAMETER TEST CONDITIONS			MIN ⁽¹⁾	TYP ⁽²⁾	MAX ⁽¹⁾	UNIT
V _{OUT}	Output voltage			3.234	3.3	3.366	
			over the entire junction temperature range of operation –40°C to 125°C	3.201		3.399	V
η	Efficiency	V _{IN} = 12 V, I _{LOAD} = 5 A		86%			

- (1) All room temperature limits are 100% tested during production with T_A = T_J = 25°C. All limits at temperature extremes are specified through correlation using standard Quality Control (SQC) methods. All limits are used to calculate Average Outgoing Quality Level (AOQL).
- (2) Typical values are determined with T_A = T_J = 25°C and represent the most likely norm.

6.6 Electrical Characteristics – 5 V

PARAMETER TEST CONDITIONS			MIN ⁽¹⁾	TYP ⁽²⁾	MAX ⁽¹⁾	UNIT	
V _{OUT}	Output voltage	V _{IN} = 8 V to 40 V, 100 mA ≤ I _{OUT} ≤ 5 A		4.9	5	5.1	
			over the entire junction temperature range of operation –40°C to 125°C	4.85		5.15	V
η	Efficiency	V _{IN} = 12 V, I _{LOAD} = 5 A			88%		

- (1) All room temperature limits are 100% tested during production with T_A = T_J = 25°C. All limits at temperature extremes are specified through correlation using standard Quality Control (SQC) methods. All limits are used to calculate Average Outgoing Quality Level (AOQL).
- (2) Typical values are determined with $T_A = T_J = 25^{\circ}C$ and represent the most likely norm.



6.7 Electrical Characteristics - 12 V

	PARAMETER TEST CONDITIONS			MIN ⁽¹⁾	TYP ⁽²⁾	MAX ⁽¹⁾	UNIT
V _{OUT}	Output voltage	V _{IN} = 15 V to 40 V, 100 mA ≤ I _{OUT} ≤ 5 A		11.76	12	12.24	V
			over the entire junction temperature range of operation –40°C to 125°C	11.64		12.36	
η	Efficiency	V _{IN} = 24 V, I _{LOAD} = 5 A		94%			

⁽¹⁾ All room temperature limits are 100% tested during production with T_A = T_J = 25°C. All limits at temperature extremes are specified through correlation using standard Quality Control (SQC) methods. All limits are used to calculate Average Outgoing Quality Level (AOQL).

6.8 Electrical Characteristics – All Output Voltage Versions


Specifications are for $T_A = T_J = 25$ °C unless otherwise specified. Unless otherwise specified $V_{IN} = 12$ V for the 3.3 V, 5 V and Adjustable versions, and $V_{IN} = 24$ V for the 12 V version.

	PARAMETER	TI	EST CONDITIONS	MIN	TYP	MAX	UNIT	
DEVICE	PARAMETERS							
IQ	Quiescent current	V _{FEEDBACK} = 8 V for 3. V _{FEEDBACK} = 15 V for	3-V, 5-V, and ADJ versions, 12-V Versions		4.2	6	mA	
	Ctondby guiagaant				50	100		
I _{STBY}	Standby quiescent current	ON/OFF pin = 0 V	over the entire junction temperature range of operation –40°C to 125°C			150	μΑ	
				3.8	4.5	5.25		
I _{CL}	Current limit	over the entire junction -40°C to 125°C	n temperature range of operation	3.6		5.4	Α	
	Output leakage	V _{IN} = 40 V,	V _{SWITCH} = 0 V			200	μΑ	
IL	current	soft-start pin = 0 V	V _{SWITCH} = -1 V		16	15	mA	
					0.15	0.17		
R _{DS(ON)}	Switch ON-resistance	I _{SWITCH} = 5 A	over the entire junction temperature range of operation –40°C to 125°C			0.29	Ω	
			Measured at			260		
f _O	Oscillator frequency	switch pin	over the entire junction temperature range of operation –40°C to 125°C	225		280	kHz	
D	Duty cycle	Maximum duty cycle			91%			
D	Duty cycle	Minimum duty cycle			0%			
I _{BIAS}	Feedback bias current	V _{FEEDBACK} = 1.3 V, AD	DJ version only		85		nΑ	
	ON/OFF threshold				1.4			
V _{ON/OFF}	voltage	over the entire junction -40°C to 125°C	n temperature range of operation	0.8		2	V	
					20			
I _{ON/OFF}	ON/OFF input current	ON/OFF pin = 0 V	over the entire junction temperature range of operation –40°C to 125°C			45	μA	
F _{SYNC}	Synchronization frequency	V_{SYNC} (pin 5) = 3.5 V,	50% duty cycle		400		kHz	
V _{SYNC}	SYNC threshold voltage				1.4		V	

⁽²⁾ Typical values are determined with $T_A = T_J = 25$ °C and represent the most likely norm.




6.9 Typical Characteristics




TEXAS INSTRUMENTS

Typical Characteristics (continued)





Typical Characteristics (continued)




1 μ sec/Div

Discontinuous Mode Switching Waveforms V_{IN} = 20 V, V_{OUT} = 5 V, I_{LOAD} = 500 mA L = 10 μ H, C_{OUT} = 400 μ F, C_{OUT}ESR = 13 m Ω A: V_{SW} Pin Voltage, 10 V/div

B: Inductor Current, 1 A/div C: Output Ripple Voltage, 20 mV/div AC-Coupled

Figure 13. Horizontal Time Base: 1 µs/div




100 μ sec/Div

Load Transient Response for Continuous Mode V $_{IN}$ = 20 V, V_{OUT} = 5 V L = 33 μ H, C_{OUT} = 200 μ F, C_{OUT} ESR = 26 m Ω

A: Output Voltage, 100 mV//div, AC-Coupled B: Load Current: 500-mA to 3-A Load Pulse

Figure 14. Horizontal Time Base: 100 µs/div



200 μsec/Div

Load Transient Response for Discontinuous Mode V_{IN} = 20 V, V_{OUT} = 5 V, L = 10 μ H, C_{OUT} = 400 μ F, C_{OUT} ESR = 13 $m\Omega$ A: Output Voltage, 100 mV/div, AC-Coupled

B: Load Current: 200-mA to 3-A Load Pulse

Figure 15. Horizontal Time Base: 200 µs/div




7 Detailed Description

7.1 Overview

The LM2670 provides all of the active functions required for a step-down (buck) switching regulator. The internal power switch is a DMOS power MOSFET to provide power supply designs with high current capability, up to 3 A, and highly efficient operation.

The design support WEBENCH, can also be used to provide instant component selection, circuit performance calculations for evaluation, a bill of materials component list and a circuit schematic for LM2670.

7.2 Functional Block Diagram



- * Active Inductor Patent Number 5,514,947
- † Active Capacitor Patent Number 5,382,918

7.3 Feature Description

7.3.1 Switch Output

This is the output of a power MOSFET switch connected directly to the input voltage. The switch provides energy to an inductor, an output capacitor, and the load circuitry under control of an internal pulse-width-modulator (PWM). The PWM controller is internally clocked by a fixed 260-kHz oscillator. In a standard step-down application the duty cycle (Time ON/Time OFF) of the power switch is proportional to the ratio of the power supply output voltage to the input voltage. The voltage on pin 1 switches between V_{IN} (switch ON) and below ground by the voltage drop of the external Schottky diode (switch OFF).



Feature Description (continued)

7.3.2 Input

The input voltage for the power supply is connected to pin 2. In addition to providing energy to the load the input voltage also provides bias for the internal circuitry of the LM2670. For ensured performance the input voltage must be in the range of 8 V to 40 V. For best performance of the power supply the input pin must always be bypassed with an input capacitor located close to pin 2.

7.3.3 C Boost

A capacitor must be connected from pin 3 to the switch output, pin 1. This capacitor boosts the gate drive to the internal MOSFET above V_{IN} to fully turn it ON. This minimizes conduction losses in the power switch to maintain high efficiency. The recommended value for C Boost is 0.01 μ F.

7.3.4 Ground

This is the ground reference connection for all components in the power supply. In fast-switching, high-current applications such as those implemented with the LM2670, TI recommends using a broad ground plane to minimize signal coupling throughout the circuit.

7.3.5 SYNC

This input allows control of the switching clock frequency. If left open-circuited the regulator will be switched at the internal oscillator frequency, between 225 kHz and 280 kHz. An external clock can be used to force the switching frequency and thereby control the output ripple frequency of the regulator. This capability provides for consistent filtering of the output ripple from system to system as well as precise frequency spectrum positioning of the ripple frequency which is often desired in communications and radio applications. This external frequency must be greater than the LM2670 internal oscillator frequency, which could be as high as 280 kHz, to prevent an erroneous reset of the internal ramp oscillator and PWM control of the power switch. The ramp oscillator is reset on the positive going edge of the sync input signal. TI recommends that the external TTL or CMOS compatible clock (between 0 V and a level greater than 3 V) be AC-coupled to the sync input through a 100-pf capacitor and a 1-k Ω resistor to ground at pin 5 as shown in Figure 21.

When the SYNC function is used, current limit frequency foldback is not active. Therefore, the device my not be fully protected against extreme output short-circuit conditions. See *Additional Application Information*.

7.3.6 Feedback

This is the input to a two-stage high gain amplifier, which drives the PWM controller. It is necessary to connect pin 6 to the actual output of the power supply to set the DC output voltage. For the fixed output devices (3.3-V, 5-V, and 12-V outputs), a direct wire connection to the output is all that is required as internal gain setting resistors are provided inside the LM2670. For the adjustable output version two external resistors are required to set the DC output voltage. For stable operation of the power supply it is important to prevent coupling of any inductor flux to the feedback input.

7.3.7 ON/OFF

This input provides an electrical ON/OFF control of the power supply. Connecting this pin to ground or to any voltage less than 0.8 V will completely turn OFF the regulator. The current drain from the input supply when OFF is only 50 μ A. Pin 7 has an internal pull-up current source of approximately 20 μ A and a protection clamp Zener diode of 7 V to ground. When electrically driving the ON/OFF pin the high voltage level for the ON condition should not exceed the 6-V absolute maximum limit. When ON/OFF control is not required pin 7 should be left open circuited.



7.4 Device Functional Modes

7.4.1 Shutdown Mode

The ON/ $\overline{\text{OFF}}$ pin provides electrical ON and OFF control for the LM2670. When the voltage of this pin is lower than 1.4 V, the device is shutdown mode. The typical standby current in this mode is 50 μ A.

7.4.2 Active Mode

When the voltage of the ON/OFF pin is higher than 1.4 V, the device starts switching and the output voltage rises until it reaches a normal regulation voltage.



8 Application and Implementation

NOTE

Information in the following applications sections is not part of the TI component specification, and TI does not warrant its accuracy or completeness. TI's customers are responsible for determining suitability of components for their purposes. Customers should validate and test their design implementation to confirm system functionality.

8.1 Application Information

8.1.1 Design Considerations

Power supply design using the LM2670 is greatly simplified by using recommended external components. A wide range of inductors, capacitors and Schottky diodes from several manufacturers have been evaluated for use in designs that cover the full range of capabilities (input voltage, output voltage, and load current) of the LM2670. A simple design procedure using nomographs and component tables provided in this data sheet leads to a working design with very little effort.

The individual components from the various manufacturers called out for use are still just a small sample of the vast array of components available in the industry. While these components are recommended, they are not exclusively the only components for use in a design. After a close comparison of component specifications, equivalent devices from other manufacturers could be substituted for use in an application.

Important considerations for each external component and an explanation of how the nomographs and selection tables were developed follows.

8.1.2 Inductor

The inductor is the key component in a switching regulator. For efficiency the inductor stores energy during the switch ON time and then transfers energy to the load while the switch is OFF.

Nomographs are used to select the inductance value required for a given set of operating conditions. The nomographs assume that the circuit is operating in continuous mode (the current flowing through the inductor never falls to zero). The magnitude of inductance is selected to maintain a maximum ripple current of 30% of the maximum load current. If the ripple current exceeds this 30% limit the next larger value is selected.

The inductors offered have been specifically manufactured to provide proper operation under all operating conditions of input and output voltage and load current. Several part types are offered for a given amount of inductance. Both surface mount and through-hole devices are available. The inductors from each of the three manufacturers have unique characteristics.

- Renco: ferrite stick core inductors; benefits are typically lowest cost and can withstand ripple and transient
 peak currents above the rated value. These inductors have an external magnetic field, which may generate
 EMI.
- Pulse Engineering: powdered iron toroid core inductors; these also can withstand higher than rated currents and, being toroid inductors, have low EMI.
- Coilcraft: ferrite drum core inductors; these are the smallest physical size inductors and are available only as surface mount components. These inductors also generate EMI but less than stick inductors.

8.1.3 Output Capacitor

The output capacitor acts to smooth the DC output voltage and also provides energy storage. Selection of an output capacitor, with an associated equivalent series resistance (ESR), impacts both the amount of output ripple voltage and stability of the control loop.

The output ripple voltage of the power supply is the product of the capacitor ESR and the inductor ripple current. The capacitor types recommended in the tables were selected for having low ESR ratings.

In addition, both surface mount tantalum capacitors and through-hole aluminum electrolytic capacitors are offered as solutions.



Application Information (continued)

Impacting frequency stability of the overall control loop, the output capacitance, in conjunction with the inductor, creates a double pole inside the feedback loop. In addition the capacitance and the ESR value create a zero. These frequency response effects together with the internal frequency compensation circuitry of the LM2670 modify the gain and phase shift of the closed-loop system.

As a general rule for stable switching regulator circuits it is desired to have the unity gain bandwidth of the circuit to be limited to no more than one-sixth of the controller switching frequency. With the fixed 260-kHz switching frequency of the LM2670, the output capacitor is selected to provide a unity gain bandwidth of 40 kHz maximum. Each recommended capacitor value has been chosen to achieve this result.

In some cases multiple capacitors are required either to reduce the ESR of the output capacitor, to minimize output ripple (a ripple voltage of 1% of V_{OUT} or less is the assumed performance condition), or to increase the output capacitance to reduce the closed loop unity gain bandwidth (to less than 40 kHz). When parallel combinations of capacitors are required it has been assumed that each capacitor is the exact same part type.

The RMS current and working voltage (WV) ratings of the output capacitor are also important considerations. In a typical step-down switching regulator, the inductor ripple current (set to be no more than 30% of the maximum load current by the inductor selection) is the current that flows through the output capacitor. The capacitor RMS current rating must be greater than this ripple current. The voltage rating of the output capacitor must be greater than 1.3 times the maximum output voltage of the power supply. If operation of the system at elevated temperatures is required, the capacitor voltage rating may be de-rated to less than the nominal room temperature rating. Careful inspection of the manufacturer's specification for de-rating of working voltage with temperature is important.

8.1.4 Input Capacitor

Fast changing currents in high current switching regulators place a significant dynamic load on the unregulated power source. An input capacitor helps to provide additional current to the power supply as well as smooth out input voltage variations.

Like the output capacitor, the key specifications for the input capacitor are RMS current rating and working voltage. The RMS current flowing through the input capacitor is equal to one-half of the maximum DC load current so the capacitor should be rated to handle this. Paralleling multiple capacitors proportionally increases the current rating of the total capacitance. The voltage rating must also be selected to be 1.3 times the maximum input voltage. Depending on the unregulated input power source, under light load conditions the maximum input voltage could be significantly higher than normal operation. Consider when selecting an input capacitor.

The input capacitor must be placed very close to the input pin of the LM2670. Due to relative high current operation with fast transient changes, the series inductance of input connecting wires or PCB traces can create ringing signals at the input terminal which could possibly propagate to the output or other parts of the circuitry. It may be necessary in some designs to add a small valued (0.1 μ F to 0.47 μ F) ceramic type capacitor in parallel with the input capacitor to prevent or minimize any ringing.

8.1.5 Catch Diode

When the power switch in the LM2670 turns OFF, the current through the inductor continues to flow. The path for this current is through the diode connected between the switch output and ground. This forward biased diode clamps the switch output to a voltage less than ground. This negative voltage must be greater than –1 V so a low voltage drop (particularly at high current levels) Schottky diode is recommended. Total efficiency of the entire power supply is significantly impacted by the power lost in the output catch diode. The average current through the catch diode is dependent on the switch duty cycle (D) and is equal to the load current times (1-D). Use of a diode rated for much higher current than is required by the actual application helps to minimize the voltage drop and power loss in the diode.

During the switch ON time the diode is reversed biased by the input voltage. The reverse voltage rating of the diode must be at least 1.3 times greater than the maximum input voltage.

8.1.6 Boost Capacitor

The boost capacitor creates a voltage used to overdrive the gate of the internal power MOSFET. This improves efficiency by minimizing the on resistance of the switch and associated power loss. For all applications, TI recommends using a 0.01-µF, 50-V ceramic capacitor.



Application Information (continued)

8.1.7 Sync Components

When synchronizing the LM2670 with an external clock it is recommended to connect the clock to pin 5 through a series 100-pf capacitor and connect a $1-k\Omega$ resistor to ground from pin 5. This RC network creates a short 100-ns pulse on each positive edge of the clock to reset the internal ramp oscillator. The reset time of the oscillator is approximately 300 ns.

8.1.8 Additional Application Information

When the output voltage is greater than approximately 6 V, and the duty cycle at minimum input voltage is greater than approximately 50%, the designer should exercise caution in selection of the output filter components. When an application designed to these specific operating conditions is subjected to a current limit fault condition, it may be possible to observe a large hysteresis in the current limit. This can affect the output voltage of the device until the load current is reduced sufficiently to allow the current limit protection circuit to reset itself.

Under current limiting conditions, the LM267x is designed to respond in the following manner:

- 1. At the moment when the inductor current reaches the current limit threshold, the ON-pulse is immediately terminated. This happens for any application condition.
- 2. However, the current limit block is also designed to momentarily reduce the duty cycle to below 50% to avoid subharmonic oscillations, which could cause the inductor to saturate.
- 3. Thereafter, once the inductor current falls below the current limit threshold, there is a small relaxation time during which the duty cycle progressively rises back above 50% to the value required to achieve regulation.

If the output capacitance is sufficiently *large*, it may be possible that as the output tries to recover, the output capacitor charging current is large enough to repeatedly re-trigger the current limit circuit before the output has fully settled. This condition is exacerbated with higher output voltage settings because the energy requirement of the output capacitor varies as the square of the output voltage (½ CV²), thus requiring an increased charging current.

A simple test to determine if this condition might exist for a suspect application is to apply a short circuit across the output of the converter, and then remove the shorted output condition. In an application with properly selected external components, the output recovers smoothly.

Practical values of external components that have been experimentally found to work well under these specific operating conditions are $C_{OUT}=47~\mu F$, $L=22~\mu H$. It should be noted that even with these components, for a device's current limit of I_{CLIM} , the maximum load current under which the possibility of the large current limit hysteresis can be minimized is I_{CLIM} / 2. For example, if the input is 24 V and the set output voltage is 18 V, then for a desired maximum current of 1.5 A, the current limit of the chosen switcher must be confirmed to be at least 3 A.

Under extreme overcurrent or short-circuit conditions, the LM267X employs frequency foldback in addition to the current limit. If the cycle-by-cycle inductor current increases above the current limit threshold (due to short circuit or inductor saturation for example) the switching frequency is automatically reduced to protect the IC. Frequency below 100 kHz is typical for an extreme short-circuit condition.

8.2 Typical Applications

8.2.1 Typical Application for All Output Voltage Versions




Figure 16. Basic Circuit for All Output Voltage Versions

8.2.1.1 Design Requirements

Select the power supply operating conditions and the maximum output current and follow below procedures to find the external components for LM2670

8.2.1.2 Detailed Design Procedure

Using the nomographs and tables in this data sheet (or use the available design software at www.ti.com) a complete step-down regulator can be designed in a few simple steps.

Step 1: Define the power supply operating conditions:

- Required output voltage
- Maximum DC input voltage
- Maximum output load current

Step 2: Set the output voltage by selecting a fixed output LM2670 (3.3-V, 5-V, or 12-V applications) or determine the required feedback resistors for use with the adjustable LM2670–ADJ

Step 3: Determine the inductor required by using one of the four nomographs, Figure 17 through Figure 20. Table 3 provides a specific manufacturer and part number for the inductor.

Step 4: Using Table 5 and Table 6 (fixed output voltage) or Table 9 and Table 10 (adjustable output voltage), determine the output capacitance required for stable operation. Table 1 or Table 2 provide the specific capacitor type from the manufacturer of choice.

Step 5: Determine an input capacitor from Table 7 or Table 8 for fixed output voltage applications. Use Table 1 or Table 2 to find the specific capacitor type. For adjustable output circuits select a capacitor from Table 1 or Table 2 with a sufficient working voltage (WV) rating greater than V_{IN} max, and an RMS current rating greater than one-half the maximum load current (2 or more capacitors in parallel may be required).

Step 6: Select a diode from Table 4. The current rating of the diode must be greater than I_{LOAD} max and the reverse voltage rating must be greater than V_{IN} max.

Step 7: Include a 0.01- μ F, 50-V capacitor for C_{BOOST} in the design.



Typical Applications (continued)

8.2.1.2.1 Capacitor Selection Guides

Table 1. Input and Output Capacitor Codes—Surface Mount

CAPACITOR				S	SURFACE MOUN	NT			
REFERENCE		AVX TPS SERIE	S	SPR	AGUE 594D SE	RIES	KE	MET T495 SER	IES
CODE	C (µF)	WV (V)	Irms (A)	C (µF)	WV (V)	Irms (A)	C (µF)	WV (V)	Irms (A)
C1	330	6.3	1.15	120	6.3	1.1	100	6.3	0.82
C2	100	10	1.1	220	6.3	1.4	220	6.3	1.1
C3	220	10	1.15	68	10	1.05	330	6.3	1.1
C4	47	16	0.89	150	10	1.35	100	10	1.1
C5	100	16	1.15	47	16	1	150	10	1.1
C6	33	20	0.77	100	16	1.3	220	10	1.1
C7	68	20	0.94	180	16	1.95	33	20	0.78
C8	22	25	0.77	47	20	1.15	47	20	0.94
C9	10	35	0.63	33	25	1.05	68	20	0.94
C10	22	35	0.66	68	25	1.6	10	35	0.63
C11	_	_	_	15	35	0.75	22	35	0.63
C12	_	_	_	33	35	1	4.7	50	0.66
C13	_	_	_	15	50	0.9	_	_	_

Table 2. Input and Output Capacitor Codes—Through Hole

CAPACITOR						THROUG	H HOLE					
REFERENCE	SANYO	OS-CON SA	SERIES	SANY	O MV-GX S	ERIES	NICH	ICON PL SI	ERIES	PANAS	ONIC HFQ	SERIES
CODE	C (µF)	WV (V)	Irms (A)	C (µF)	WV (V)	Irms (A)	C (µF)	WV (V)	Irms (A)	C (µF)	WV (V)	Irms (A)
C1	47	6.3	1	1000	6.3	0.8	680	10	0.8	82	35	0.4
C2	150	6.3	1.95	270	16	0.6	820	10	0.98	120	35	0.44
C3	330	6.3	2.45	470	16	0.75	1000	10	1.06	220	35	0.76
C4	100	10	1.87	560	16	0.95	1200	10	1.28	330	35	1.01
C5	220	10	2.36	820	16	1.25	2200	10	1.71	560	35	1.4
C6	33	16	0.96	1000	16	1.3	3300	10	2.18	820	35	1.62
C7	100	16	1.92	150	35	0.65	3900	10	2.36	1000	35	1.73
C8	150	16	2.28	470	35	1.3	6800	10	2.68	2200	35	2.8
C9	100	20	2.25	680	35	1.4	180	16	0.41	56	50	0.36
C10	47	25	2.09	1000	35	1.7	270	16	0.55	100	50	0.5
C11	_	_	_	220	63	0.76	470	16	0.77	220	50	0.92
C12	_	_	_	470	63	1.2	680	16	1.02	470	50	1.44
C13	_	_	_	680	63	1.5	820	16	1.22	560	50	1.68
C14	_	_	_	1000	63	1.75	1800	16	1.88	1200	50	2.22
C15	_	_	_	_	_	_	220	25	0.63	330	63	1.42
C16	_	_	_	_	_	_	220	35	0.79	1500	63	2.51
C17	_	_	_	_	_	_	560	35	1.43	_	_	_
C18	_	_	_	_	_	_	2200	35	2.68	-	_	_
C19	_	_	_	_	_	_	150	50	0.82	_	_	_
C20	_	_	_	_	_	_	220	50	1.04	-	_	_
C21	_	_	_	_	_	_	330	50	1.3	-	_	_
C22	_	_	_	_	_	_	100	63	0.75	_	_	_
C23	_	_		_	_	_	390	63	1.62	1	_	_
C24	_	_	_	_	_	_	820	63	2.22	ı	_	_
C25	_	_	_	_	_	_	1200	63	2.51	1	_	_



8.2.1.2.2 Inductor Selection Guides

For Continuous Mode Operation

Table 3. Inductor Manufacturer Part Numbers


INDUCTOR			RENO	0	PULSE EN	GINEERING	COILCRAFT
REFERENC E NUMBER	INDUCTANCE (µH)	CURRENT (A)	THROUGH HOLE	SURFACE MOUNT	THROUGH HOLE	SURFACE MOUNT	SURFACE MOUNT
L23	33	1.35	RL-5471-7	RL1500-33	PE-53823	PE-53823S	DO3316-333
L24	22	1.65	RL-1283-22-43	RL1500-22	PE-53824	PE-53824S	DO3316-223
L25	15	2	RL-1283-15-43	RL1500-15	PE-53825	PE-53825S	DO3316-153
L29	100	1.41	RL-5471-4	RL-6050-100	PE-53829	PE-53829S	DO5022P-104
L30	68	1.71	RL-5471-5	RL6050-68	PE-53830	PE-53830S	DO5022P-683
L31	47	2.06	RL-5471-6	RL6050-47	PE-53831	PE-53831S	DO5022P-473
L32	33	2.46	RL-5471-7	RL6050-33	PE-53932	PE-53932S	DO5022P-333
L33	22	3.02	RL-1283-22-43	RL6050-22	PE-53933	PE-53933S	DO5022P-223
L34	15	3.65	RL-1283-15-43	_	PE-53934	PE-53934S	DO5022P-153
L38	68	2.97	RL-5472-2	_	PE-54038	PE-54038S	_
L39	47	3.57	RL-5472-3	_	PE-54039	PE-54039S	_
L40	33	4.26	RL-1283-33-43	_	PE-54040	PE-54040S	_
L41	22	5.22	RL-1283-22-43	_	PE-54041	P0841	_
L44	68	3.45	RL-5473-3	_	PE-54044	_	_
L45	10	4.47	RL-1283-10-43	_	_	P0845	DO5022P-103HC

Table 4. Schottky Diode Selection Table

REVERSE	SURF	ACE MOUNT	THRO	OUGH HOLE
VOLTAGE (V)	3 A	5 A OR MORE	3 A	5 A OR MORE
20	SK32		1N5820	
20	3N32	_	SR302	_
30	SK33	MBRD835L	1N5821	
30	30WQ03F	IVIDRUOSOL	31DQ03	_
	SK34	MBRB1545CT	1N5822	_
	30BQ040		MBR340	MBR745
40	30WQ04F	CT00450	31DQ04	80SQ045
	MBRS340	6TQ045S	CD 402	CTO045
	MBRD340		SR403	6TQ045
	SK35		MBR350	
50 or more	2014/0055	_	31DQ05	_
	30WQ05F		SR305	



8.2.1.3 Application Curves



8.2.2 Fixed Output Voltage Application




Figure 21. Basic Circuit for Fixed Output Voltage Applications

Copyright © 2000–2016, Texas Instruments Incorporated Submit Documentation Feedback



8.2.2.1 Design Requirements

Select the power supply operating conditions and the maximum output current and follow below procedures to find the external components for LM2670

8.2.2.2 Detailed Design Procedure

A system logic power supply bus of 3.3 V is to be generated from a wall adapter which provides an unregulated DC voltage of 13 V to 16 V. The maximum load current is 2.5 A. Through-hole components are preferred.

Step 1: Operating conditions are:

- V_{OUT} = 3.3 V
- V_{IN} max = 16 V
- I_{I OAD} max = 2.5 A

Step 2: Select an LM2670T-3.3. The output voltage will have a tolerance of $\pm 2\%$ at room temperature and $\pm 3\%$ over the full operating temperature range.

Step 3: Use the nomograph for the 3.3-V device, Figure 17. The intersection of the 16 V horizontal line (V_{IN} max) and the 2.5 A vertical line (I_{LOAD} max) indicates that L33, a 22- μ H inductor, is required.

From Table 3, L33 in a through-hole component is available from Renco with part number RL-1283-22-43 or part number PE-53933 from Pulse Engineering.

Step 4: Use Table 5 or Table 6 to determine an output capacitor. With a 3.3-V output and a 22-µH inductor there are four through-hole output capacitor solutions with the number of same type capacitors to be paralleled and an identifying capacitor code given. Table 1 or Table 2 provide the actual capacitor characteristics. Any of the following choices will work in the circuit:

- 1 x 220-μF, 10-V Sanyo OS-CON (code C5)
- 1 x 1000-μF, 35-V Sanyo MV-GX (code C10)
- 1 x 2200-μF, 10-V Nichicon PL (code C5)
- 1 x 1000-µF, 35-V Panasonic HFQ (code C7)

Step 5: Use Table 7 or Table 8 to select an input capacitor. With 3.3-V output and 22 μH there are three through-hole solutions. These capacitors provide a sufficient voltage rating and an rms current rating greater than 1.25 A (1/2 I_{LOAD} max). Again using Table 1 or Table 2 for specific component characteristics the following choices are suitable:

- 1 x 1000-µF, 63-V Sanyo MV-GX (code C14)
- 1 x 820-μF, 63-V Nichicon PL (code C24)
- 1 x 560-µF, 50-V Panasonic HFQ (code C13)

Step 6: From Table 4 a 3-A Schottky diode must be selected. For through-hole components 20-V rated diodes are sufficient. and 2 part types are suitable:

- 1N5820
- SR302

Step 7: A 0.01-µF capacitor is used for C_{BOOST}.

8.2.2.2.1 Capacitor Selection Guides

Table 5. Output Capacitors for Fixed Output Voltage Application—Surface Mount (1)(2)

		SURFACE MOUNT								
OUTPUT VOLTAGE (V)	INDUCTANCE (µH)	AVX TPS	SERIES	SPRAGUE 5	94D SERIES	KEMET T4	KEMET T495 SERIES			
1021/102(1)		NO.	C CODE	NO.	C CODE	NO.	C CODE			
	10	4	C2	3	C1	4	C4			
3.3	15	4	C2	3	C1	4	C4			
3.3	22	3	C2	2	C7	3	C4			
	33	2	C2	2	C6	2	C4			

(1) No. represents the number of identical capacitor types to be connected in parallel

(2) C Code indicates the Capacitor Reference number in Table 1 or Table 2 for identifying the specific component from the manufacturer



Table 5. Output Capacitors for Fixed Output Voltage Application—Surface Mount⁽¹⁾ (continued)

OUTPUT VOLTAGE (V)				SURFAC	E MOUNT		
	INDUCTANCE (µH)	AVX TPS	S SERIES	SPRAGUE 5	94D SERIES	KEMET T	495 SERIES
1021/102(1)		NO.	C CODE	NO.	C CODE	NO.	C CODE
	10	4	C2	4	C6	4	C4
	15	3	C2	2	C7	3	C4
5	22	3	C2	2	C7	3	C4
	33	2	C2	2	C3	2	C4
	47	2	C2	1	C7	2	C4
	10	4	C5	3	C6	5	C9
	15	3	C5	2	C7	4	C8
	22	2	C5	2	C6	3	C8
12	33	2	C5	1	C7	2	C8
	47	2	C4	1	C6	2	C8
	68	1	C5	1	C5	2	C7
	100	1	C4	1	C5	1	C8

Table 6. Output Capacitors for Fixed Output Voltage Application—Through Hole (1)(2)

					THROUG	H HOLE			
OUTPUT VOLTAGE (V)	INDUCTANCE (µH)		S-CON SA RIES	SANYO MV	-GX SERIES	NICHICON	PL SERIES	PANASONIC	HFQ SERIES
		NO.	C CODE	NO.	C CODE	NO.	C CODE	NO.	C CODE
	10	1	C3	1	C10	1	C6	2	C6
2.2	15	1	C3	1	C10	1	C6	2	C5
3.3	22	1	C5	1	C10	1	C5	1	C7
	33	1	C2	1	C10	1	C13	1	C5
	10	2	C4	1	C10	1	C6	2	C5
	15	1	C5	1	C10	1	C5	1	C6
5	22	1	C5	1	C5	1	C5	1	C5
	33	1	C4	1	C5	1	C13	1	C5
	47	1	C4	1	C4	1	C13	2	C3
	10	2	C7	1	C5	1	C18	2	C5
	15	1	C8	1	C5	1	C17	1	C5
	22	1	C7	1	C5	1	C13	1	C5
12	33	1	C7	1	C3	1	C11	1	C4
	47	1	C7	1	C3	1	C10	1	C3
	68	1	C7	1	C2	1	C10	1	C3
	100	1	C7	1	C2	1	C9	1	C1

⁽¹⁾ No. represents the number of identical capacitor types to be connected in parallel

Table 7. Input Capacitors for Fixed Output Voltage Application—Surface Mount (1)(2)(3)

		SURFACE MOUNT								
OUTPUT VOLTAGE (V)	INDUCTANCE (µH)	AVX TPS SERIES		SPRAGUE 5	94D SERIES	KEMET T4	95 SERIES			
		NO.	C CODE	NO.	C CODE	NO.	C CODE			
	10	2	C5	1	C7	2	C8			
2.2	15	3	C9	1	C10		C10			
3.3	22	See ⁽⁴⁾		C12						
	33	See ⁽⁴⁾	See ⁽⁴⁾	2	C13	2	C12			

⁽¹⁾ Assumes worst case maximum input voltage and load current for a given inductance value

⁽²⁾ C Code indicates the Capacitor Reference number in Table 1 or Table 2 for identifying the specific component from the manufacturer

⁽²⁾ No. represents the number of identical capacitor types to be connected in parallel

³⁾ C Code indicates the Capacitor Reference number in Table 1 or Table 2 for identifying the specific component from the manufacturer

⁽⁴⁾ Check voltage rating of capacitors to be greater than application input voltage



Table 7. Input Capacitors for Fixed Output Voltage Application—Surface Mount $^{(0)}$ (continued)

				SURFAC	E MOUNT		
OUTPUT VOLTAGE (V)	INDUCTANCE (µH)	AVX TPS	SERIES	SPRAGUE 5	94D SERIES	KEMET T	495 SERIES
1021/102(1)		NO.	C CODE	NO.	C CODE	NO.	C CODE
	10	2	C5	1	C7	2	C8
	15	2	C5	1	C7	2	C8
5	22	3	C10	2	C12	3	C11
	33	See ⁽⁴⁾	See ⁽⁴⁾	2	C13	3	C12
	47	See ⁽⁴⁾	See ⁽⁴⁾	1	C13	2	C12
	10	2	C7	2	C10	2	C7
	15	2	C7	2	C10	2	C7
	22	3	C10	2	C12	3	C10
12	33	3	C10	2	C12	3	C10
	47	See ⁽⁴⁾	See ⁽⁴⁾	2	C13	3	C12
	68	See ⁽⁴⁾	See ⁽⁴⁾	2	C13	2	C12
	100	See ⁽⁴⁾	See ⁽⁴⁾	1	C13	2	C12

Table 8. Input Capacitors for Fixed Output Voltage Application—Through Hole⁽¹⁾⁽²⁾⁽³⁾

					THROU	JGH HOLE			
OUTPUT VOLTAGE (V)	INDUCTANCE (µH)		OS-CON SA RIES	SANYO MV	V-GX SERIES NICHICO		PL SERIES	PANASONIC	C HFQ SERIES
		NO.	C CODE	NO.	C CODE	NO.	C CODE	NO.	C CODE
	10	1	C7	2	C4	1	C5	1	C6
2.2	15	1	C10	1	C10	1	C18	1	C6
3.3	22	See ⁽⁴⁾	See ⁽⁴⁾	1	C14	1	C24	1	C13
	33	See ⁽⁴⁾	See ⁽⁴⁾	1	C12	1	C20	1	C12
	10	1	C7	2	C4	1	C14	1	C6
	15	1	C7	2	C4	1	C14	1	C6
5	22	See ⁽⁴⁾	See ⁽⁴⁾	1	C10	1	C18	1	C13
	33	See ⁽⁴⁾	See ⁽⁴⁾	1	C14	1	C23	1	C13
	47	See ⁽⁴⁾	See ⁽⁴⁾	1	C12	1	C20	1	C12
	10	1	C9	1	C10	1	C18	1	C6
	15	1	C10	1	C10	1	C18	1	C6
	22	1	C10	1	C10	1	C18	1	C6
12	33	See ⁽⁴⁾	See ⁽⁴⁾	1	C10	1	C18	1	C6
	47	See ⁽⁴⁾	See ⁽⁴⁾	1	C13	1	C23	1	C13
	68	See ⁽⁴⁾	See ⁽⁴⁾	1	C12	1	C21	1	C12
	100	See ⁽⁴⁾	See ⁽⁴⁾	1	C11	1	C22	1	C11

- (1) Assumes worst case maximum input voltage and load current for a given inductance value
 (2) No. represents the number of identical capacitor types to be connected in parallel
 (3) C Code indicates the Capacitor Reference number in Table 1 or Table 2 for identifying the specific component from the manufacturer

Product Folder Links: LM2670

Check voltage rating of capacitors to be greater than application input voltage



8.2.3 Adjustable Output Voltage Application

Locate the Programming Resistors near the Feedback Pin Using Short Leads




Figure 22. Basic Circuit for Adjustable Output Voltage Applications

8.2.3.1 Design Requirements

Select the power supply operating conditions and the maximum output current and follow below procedures to find the external components for LM2670

8.2.3.2 Detailed Design Procedure

In this example, it is desired to convert the voltage from a two battery automotive power supply (voltage range of 20 V to 28 V, typical in large truck applications) to the 14.8-VDC alternator supply typically used to power electronic equipment from single battery 12-V vehicle systems. The load current required is 2 A maximum. It is also desired to implement the power supply with all surface mount components.

Step 1: Operating conditions are:

- V_{OUT} = 14.8 V
- V_{IN} maximum = 28 V
- I_{LOAD} maximum = 2 A

Step 2: Select an LM2670S-ADJ. To set the output voltage to 14.9 V, two resistors need to be chosen (R1 and R2 in Figure 22). For the adjustable device the output voltage is set by the following relationship:

$$V_{OUT} = V_{FB} \left(1 + \frac{R_2}{R_1} \right)$$

where

V_{FB} is the feedback voltage of typically 1.21 V

A recommended value to use for R1 is 1 k Ω . In this example then R2 is determined to be:

$$R_2 = R_1 \left(\frac{V_{OUT}}{V_{FB}} - 1 \right) = 1 k\Omega \left(\frac{14.8 V}{1.21 V} - 1 \right)$$
 (2)

 $R2 = 11.23 \text{ k}\Omega$

The closest standard 1% tolerance value to use is 11.3 k Ω

This is set the nominal output voltage to 14.88 V which is within 0.5% of the target value.

Step 3: To use the nomograph for the adjustable device, Figure 20, requires a calculation of the inductor Volt • microsecond constant (E • T expressed in V • μ S) from the following formula:

$$E \cdot T = (V_{IN(MAX)} - V_{OUT} - V_{SAT}) \cdot \frac{V_{OUT} + V_D}{V_{IN(MAX)} - V_{SAT} + V_D} \cdot \frac{1000}{260} (V \cdot \mu s)$$

where



V_{SAT} is the voltage drop across the internal power switch which is R_{ds(ON)} times I_{LOAD}

(3)

In this example this would be typically 0.15 Ω × 2 A or 0.3 V and V_D is the voltage drop across the forward biased Schottky diode, typically 0.5 V. The switching frequency of 260 kHz is the nominal value to use to estimate the ON time of the switch during which energy is stored in the inductor.

For this example E • T is found to be:

E • T =
$$(28 - 14.8 - 0.3) \cdot \frac{14.8 + 0.5}{28 - 0.3 + 0.5} \cdot \frac{1000}{260} \text{ (V} \cdot \mu \text{s)}$$
 (4)

$$E \cdot T = (12.9V) \cdot \frac{15.3}{28.2} \cdot 3.85 (V \cdot \mu s) = 26.9 (V \cdot \mu s)$$
 (5)

Using Figure 20, the intersection of 27 V • μ S horizontally and the 2 A vertical line (I_{LOAD} max) indicates that L38, a 68- μ H inductor, must be used.

From Table 3, L38 in a surface mount component is available from Pulse Engineering with part number PE-54038S.

Step 4: Use Table 9 or Table 10 to determine an output capacitor. With a 14.8-V output the 12.5 to 15 V row is used and with a 68-μH inductor there are three surface mount output capacitor solutions. Table 1 or Table 2 provides the actual capacitor characteristics based on the C Code number. Any of the following choices can be used:

- 1 x 33-µF, 20-V AVX TPS (code C6)
- 1 x 47-μF, 20-V Sprague 594 (code C8)
- 1 x 47-μF, 20-V Kemet T495 (code C8)

NOTE

When using the adjustable device in low voltage applications (less than 3-V output), if the nomograph, Figure 20, selects an inductance of 22 μ H or less, Table 9 and Table 10 do not provide an output capacitor solution. With these conditions the number of output capacitors required for stable operation becomes impractical. TI recommends using either a 33- μ H or 47- μ H inductor and the output capacitors from Table 9 or Table 10.

Step 5: An input capacitor for this example will require at least a 35-V WV rating with an RMS current rating of 1 A (1/2 I_{OUT} max). From Table 1 or Table 2 it can be seen that C12, a 33-µF, 35-V capacitor from Sprague, has the required voltage and current rating of the surface mount components.

Step 6: From Table 4 a 3-A Schottky diode must be selected. For surface mount diodes with a margin of safety on the voltage rating one of five diodes can be used:

- SK34
- 30BQ040
- 30WQ04F
- MBRS340
- MBRD340

Step 7: A 0.01- μ F capacitor is used for C_{BOOST}.

24



8.2.3.2.1 Capacitor Selection Guides

Table 9. Output Capacitors for Adjustable Output Voltage Applications—Surface Mount⁽¹⁾⁽²⁾

		SURFACE MOUNT								
OUTPUT VOLTAGE (V)	INDUCTANCE	AVX TI	PS SERIES	SPRAGUE	594D SERIES	KEMET T	495 SERIES			
` '	(μH)	NO.	C CODE	NO.	C CODE	NO.	C CODE			
	33 ⁽³⁾	7	C1	6	C2	7	C3			
1.21 to 2.5	47 ⁽³⁾	5	C1	4	C2	5	C3			
	33 ⁽³⁾	4	C1	3	C2	4	C3			
2.5 to 3.75	47 ⁽³⁾	3	C1	2	C2	3	C3			
	22	4	C1	3	C2	4	C3			
3.75 to 5	33	3	C1	2	C2	3	C3			
	47	2	C1	2	C2	2	C3			
	22	3	C2	1	C3	3	C4			
	33	2	C2	2	C3	2	C4			
5 to 6.25	47	2	C2	2	C3	2	C4			
	68	1	C2	1	C3	1	C4			
	22	3	C2	1	C4	3	C4			
	33	2	C2	1	C3	2	C4			
6.25 to 7.5	47	1	C3	1	C4	1	C6			
	68	1	C2	1	C3	1	C4			
	33	2	C5	1	C6	2	C8			
	47	1	C5	1	C6	2	C8			
7.5 to 10	68	1	C5	1	C6	1	C8			
	100	1	C4	1	C5	1	C8			
	33	1	C5	1	C6	2	C8			
	47	1	C5	1	C6	2	C8			
10 to 12.5	68	1	C5	1	C6	1	C8			
	100	1	C5	1	C6	1	C8			
	33	1	C6	1	C8	1	C8			
	47	1	C6	1	C8	1	C8			
12.5 to 15	68	1	C6	1	C8	1	C8			
	100	1	C6	1	C8	1	C8			
	33	1	C8	1	C10	2	C10			
	47	1	C8	1	C9	2	C10			
15 to 20	68	1	C8	1	C9	2	C10			
	100	1	C8	1	C9	1	C10			
	33	2	C9	2	C11	2	C11			
	47	1	C10	1	C12	1	C11			
20 to 30	68	1	C9	1	C12	1	C11			
	100	1	C9	1	C12	1	C11			
	10		- I	4	C13	8	C12			
	15			3	C13	5	C12			
	22			2	C13	4	C12			
30 to 37	33	No Valu	es Available	1	C13	3	C12			
	47			1	C13	2	C12			
	68			1	C13	2	C12			

⁽¹⁾ No. represents the number of identical capacitor types to be connected in parallel

²⁾ C Code indicates the Capacitor Reference number in Table 1 or Table 2 for identifying the specific component from the manufacturer

Set to a higher value for a practical design solution.



Table 10. Output Capacitors for Adjustable Output Voltage Applications—Through Hole⁽¹⁾⁽²⁾

			THROUGH HOLE									
OUTPUT VOLTAGE (V)	INDUCTANCE (µH)		OS-CON SA RIES	SANYO M	V-GX SERIES		N PL SERIES		ONIC HFQ RIES			
		NO.	C CODE	NO.	C CODE	NO.	C CODE	NO.	C CODE			
1.21 to 2.5 2.5 to 3.75 3.75 to 5 5 to 6.25 6.25 to 7.5 7.5 to 10	33 ⁽³⁾	2	C3	5	C1	5	C3	3	С			
1.21 to 2.5	47 ⁽³⁾	2	C2	4	C1	3	C3	2	C5			
	33 ⁽³⁾	1	C3	3	C1	3	C1	2	C5			
2.5 to 3.75	47 ⁽³⁾	1	C2	2	C1	2	C3	1	C5			
	22	1	СЗ	3	C1	3	C1	2	C5			
3.75 to 5	33	1	C2	2	C1	2	C1	1	C5			
	47	1	C2	2	C1	1	C3	SE NO. 3 2 2 1 1 2	C5			
	22	1	C5	2	C6	2	С3	2	C5			
	33	1	C4	1	C6	2	C1	1	C5			
5 to 6.25	47	1	C4	1	C6	1	C3	1	C5			
	68	1	C4	1	C6	1	C1	1	C5			
(V) 1.21 to 2.5 2.5 to 3.75 3.75 to 5 5 to 6.25 6.25 to 7.5	22	1	C5	1	C6	2	C1		C5			
	33	1	C4	1	C6	1	C3		C5			
6.25 to 7.5	47	1	C4	1	C6	1	C1		C5			
	68	1	C4	1	C2	1	C1		C5			
	33	1	C7	1	C6	1			C5			
	47	1	C7	1	C6	1			C5			
7.5 to 10	68	1	C7	1	C2	1	C14 1 C14 1 C14 1 C14 1	C2				
	100	1	C7	1	C2	1		SE NO. 3 2 2 1 1 2 1 1 1 1 1 1 1 1 1 1 1 1 1	C2			
								SI NO. 3 2 2 1 1 2 1 1 1 1 1 1 1 1 1 1 1 1 1	C5			
			C5									
10 to 12.5	68	1	C7	1	C2	1	C9		C2			
	100	1	C7	1	C2	1	C9	SENO. 3 2 1 2 1 1 2 1 1 1 1 1 1 1 1 1 1 1 1	C2			
	33	1	C9	1	C10	1	C15		C2			
	47	1	C9	1	C10	1	C15		C2			
12.5 to 15	68	1	C9	1	C10	1	C15	SEF SEF SODE NO.	C2			
	100	1	C9	1	C10	1	C15		C2			
	33	1	C10	1	C7	1	C15		C2			
	47	1	C10	1	C7	1	C15		C2			
15 to 20	68	1	C10	1	C7	1	C15		C2			
	100	1	C10	1	C7	1	C15	2 2 1 2 1 1 2 1 1 1 1 1 1 1 1 1 1 1 1 1	C2			
	33	•	0.10	1	C7	1	C16		C2			
	47			1	C7	1	C16		C2			
20 to 30	68	No Value	es Available	1	C7	1	C16		C2			
	100			1	C7	1	C16	NO. 3 2 2 1 1 2 1 1 1 1 1 1 1 1 1 1 1 1 1	C2			
	10			1	C12	1	C20		C10			
	15			1	C11	1	C20		C11			
	22			1	C11	1	C20		C10			
30 to 37	33	No Value	es Available	1	C11	1	C20		C10			
	47			1	C11	1			C10			
	68			1	C11	1			C10			

⁽¹⁾ No. represents the number of identical capacitor types to be connected in parallel

9 Power Supply Recommendations

The LM2670 is designed to operate from an input voltage supply up to 40 V. This input supply must be well regulated and able to withstand maximum input current and maintain a stable voltage.

Submit Documentation Feedback

Copyright © 2000–2016, Texas Instruments Incorporated

⁽²⁾ C Code indicates the Capacitor Reference number in Table 1 or Table 2 for identifying the specific component from the manufacturer

⁽³⁾ Set to a higher value for a practical design solution.



10 Layout

10.1 Layout Guidelines

Board layout is critical for the proper operation of switching power supplies. First, the ground plane area must be sufficient for thermal dissipation purposes. Second, appropriate guidelines must be followed to reduce the effects of switching noise. Switch mode converters are very fast switching devices. In such cases, the rapid increase of input current combined with the parasitic trace inductance generates unwanted L di/dt noise spikes. The magnitude of this noise tends to increase as the output current increases. This noise may turn into electromagnetic interference (EMI) and can also cause problems in device performance. Therefore, take care in layout to minimize the effect of this switching noise. The most important layout rule is to keep the AC current loops as small as possible. Figure 23 shows the current flow in a buck converter. The top schematic shows a dotted line which represents the current flow during the top switch ON-state. The middle schematic shows the current flow during the top switch OFF-state. The bottom schematic shows the currents referred to as ac currents. These AC currents are the most critical because they are changing in a very short time period. The dotted lines of the bottom schematic are the traces to keep as short and wide as possible. This also yields a small loop area reducing the loop inductance. To avoid functional problems due to layout, review the PCB layout example. Best results are achieved if the placement of the LM2679 device, the bypass capacitor, the Schottky diode, RFBB, RFBT, and the inductor are placed as shown in the example. Note that, in the layout shown, R1 = RFBB and R2 = RFBT. TI also recommends using 2-oz. copper boards or heavier to help thermal dissipation and to reduce the parasitic inductances of board traces. See application note AN-1229 SIMPLE SWITCHER® PCB Layout Guidelines for more information.




Figure 23. Typical Current Flow on a Buck Converter

10.2 Layout Example




Figure 24. Top Layer Foil Pattern of Printed-Circuit Board



11 Device and Documentation Support

11.1 Device Support

11.1.1 Third-Party Products Disclaimer

TI'S PUBLICATION OF INFORMATION REGARDING THIRD-PARTY PRODUCTS OR SERVICES DOES NOT CONSTITUTE AN ENDORSEMENT REGARDING THE SUITABILITY OF SUCH PRODUCTS OR SERVICES OR A WARRANTY, REPRESENTATION OR ENDORSEMENT OF SUCH PRODUCTS OR SERVICES, EITHER ALONE OR IN COMBINATION WITH ANY TI PRODUCT OR SERVICE.

11.2 Related Documentation

For related documentation see the following:

- AN-1187 Leadless Leadfram Package (LLP)
- AN-1229 SIMPLE SWITCHER® PCB Layout Guidelines

11.3 Receiving Notification of Documentation Updates

To receive notification of documentation updates, navigate to the device product folder on ti.com. In the upper right corner, click on *Alert me* to register and receive a weekly digest of any product information that has changed. For change details, review the revision history included in any revised document.

11.4 Community Resources

The following links connect to TI community resources. Linked contents are provided "AS IS" by the respective contributors. They do not constitute TI specifications and do not necessarily reflect TI's views; see TI's Terms of Lise

TI E2E™ Online Community TI's Engineer-to-Engineer (E2E) Community. Created to foster collaboration among engineers. At e2e.ti.com, you can ask questions, share knowledge, explore ideas and help solve problems with fellow engineers.

Design Support *TI's Design Support* Quickly find helpful E2E forums along with design support tools and contact information for technical support.

11.5 Trademarks

E2E is a trademark of Texas Instruments.

SIMPLE SWITCHER is a registered trademark of Texas Instruments.

All other trademarks are the property of their respective owners.

11.6 Electrostatic Discharge Caution



These devices have limited built-in ESD protection. The leads should be shorted together or the device placed in conductive foam during storage or handling to prevent electrostatic damage to the MOS gates.

11.7 Glossary

SLYZ022 — TI Glossary.

This glossary lists and explains terms, acronyms, and definitions.

12 Mechanical, Packaging, and Orderable Information

The following pages include mechanical, packaging, and orderable information. This information is the most current data available for the designated devices. This data is subject to change without notice and revision of this document. For browser-based versions of this data sheet, refer to the left-hand navigation.

12.1 DAP (VSON Package)

The Die Attach Pad (DAP) can and must be connected to PCB Ground plane or island. For CAD and assembly guidelines see Application Note AN-1187 at www.ti.com/lsds/ti/analog/powermanagement/power_portal.page.

Copyright © 2000–2016, Texas Instruments Incorporated





16-Feb-2016

PACKAGING INFORMATION

Orderable Device	Status	Package Type	Package	Pins	Package	Eco Plan	Lead/Ball Finish	MSL Peak Temp	Op Temp (°C)	Device Marking	Samples
	(1)		Drawing		Qty	(2)	(6)	(3)		(4/5)	
LM2670S-12/NOPB	ACTIVE	DDPAK/ TO-263	KTW	7	45	Pb-Free (RoHS Exempt)	CU SN	Level-3-245C-168 HR	-40 to 125	LM2670 S-12	Samples
LM2670S-3.3/NOPB	ACTIVE	DDPAK/ TO-263	KTW	7	45	Pb-Free (RoHS Exempt)	CU SN	Level-3-245C-168 HR	-40 to 125	LM2670 S-3.3	Samples
LM2670S-5.0	NRND	DDPAK/ TO-263	KTW	7	45	TBD	Call TI	Call TI	-40 to 125	LM2670 S-5.0	
LM2670S-5.0/NOPB	ACTIVE	DDPAK/ TO-263	KTW	7	45	Pb-Free (RoHS Exempt)	CU SN	Level-3-245C-168 HR	-40 to 125	LM2670 S-5.0	Samples
LM2670S-ADJ	NRND	DDPAK/ TO-263	KTW	7	45	TBD	Call TI	Call TI Call TI		LM2670 S-ADJ	
LM2670S-ADJ/NOPB	ACTIVE	DDPAK/ TO-263	KTW	7	45	Pb-Free (RoHS Exempt)	CU SN	Level-3-245C-168 HR	-40 to 125	LM2670 S-ADJ	Samples
LM2670SD-12/NOPB	ACTIVE	VSON	NHM	14	250	Green (RoHS & no Sb/Br)	CU SN	Level-1-260C-UNLIM	-40 to 125	S0002LB	Samples
LM2670SD-3.3/NOPB	ACTIVE	VSON	NHM	14	250	Green (RoHS & no Sb/Br)	CU SN	Level-1-260C-UNLIM	-40 to 125	S0002NB	Samples
LM2670SD-5.0/NOPB	ACTIVE	VSON	NHM	14	250	Green (RoHS & no Sb/Br)	CU SN	Level-1-260C-UNLIM	-40 to 125	S0002PB	Samples
LM2670SD-ADJ/NOPB	ACTIVE	VSON	NHM	14	250	Green (RoHS & no Sb/Br)	CU SN	Level-1-260C-UNLIM	-40 to 125	S0002RB	Samples
LM2670SDX-3.3/NOPB	ACTIVE	VSON	NHM	14	2500	Green (RoHS & no Sb/Br)	CU SN	Level-1-260C-UNLIM	-40 to 125	S0002NB	Samples
LM2670SDX-5.0/NOPB	ACTIVE	VSON	NHM	14	2500	Green (RoHS & no Sb/Br)	CU SN	Level-1-260C-UNLIM	-40 to 125	S0002PB	Samples
LM2670SDX-ADJ/NOPB	ACTIVE	VSON	NHM	14	2500	Green (RoHS & no Sb/Br)	CU SN	Level-1-260C-UNLIM	-40 to 125	S0002RB	Samples
LM2670SX-12/NOPB	ACTIVE	DDPAK/ TO-263	KTW	7	500	Pb-Free (RoHS Exempt)	CU SN	Level-3-245C-168 HR	-40 to 125	LM2670 S-12	Samples
LM2670SX-3.3/NOPB	ACTIVE	DDPAK/ TO-263	KTW	7	500	Pb-Free (RoHS Exempt)	CU SN	Level-3-245C-168 HR	-40 to 125	LM2670 S-3.3	Samples
LM2670SX-5.0/NOPB	ACTIVE	DDPAK/ TO-263	KTW	7	500	Pb-Free (RoHS Exempt)	CU SN	Level-3-245C-168 HR	-40 to 125	LM2670 S-5.0	Samples
LM2670SX-ADJ	NRND	DDPAK/ TO-263	KTW	7	500	TBD	Call TI	Call TI	-40 to 125	LM2670 S-ADJ	



PACKAGE OPTION ADDENDUM

16-Feb-2016

Orderable Device	Status	Package Type	Package Drawing	Pins	Package Qty	Eco Plan	Lead/Ball Finish (6)	MSL Peak Temp	Op Temp (°C)	Device Marking (4/5)	Samples
LM2670SX-ADJ/NOPB	ACTIVE	DDPAK/ TO-263	KTW	7	500	Pb-Free (RoHS Exempt)	CU SN	Level-3-245C-168 HR	-40 to 125	LM2670 S-ADJ	Samples
LM2670T-12/NOPB	ACTIVE	TO-220	NDZ	7	45	Green (RoHS & no Sb/Br)	CU SN	Level-1-NA-UNLIM	-40 to 125	LM2670 T-12	Samples
LM2670T-3.3/NOPB	ACTIVE	TO-220	NDZ	7	45	Green (RoHS & no Sb/Br)	CU SN	Level-1-NA-UNLIM	-40 to 125	LM2670 T-3.3	Samples
LM2670T-5.0/NOPB	ACTIVE	TO-220	NDZ	7	45	Green (RoHS & no Sb/Br)	CU SN	Level-1-NA-UNLIM	-40 to 125	LM2670 T-5.0	Samples
LM2670T-ADJ/NOPB	ACTIVE	TO-220	NDZ	7	45	Green (RoHS & no Sb/Br)	CU SN	Level-1-NA-UNLIM	-40 to 125	LM2670 T-ADJ	Samples

(1) The marketing status values are defined as follows:

ACTIVE: Product device recommended for new designs.

LIFEBUY: TI has announced that the device will be discontinued, and a lifetime-buy period is in effect.

NRND: Not recommended for new designs. Device is in production to support existing customers, but TI does not recommend using this part in a new design.

PREVIEW: Device has been announced but is not in production. Samples may or may not be available.

OBSOLETE: TI has discontinued the production of the device.

(2) Eco Plan - The planned eco-friendly classification: Pb-Free (RoHS), Pb-Free (RoHS Exempt), or Green (RoHS & no Sb/Br) - please check http://www.ti.com/productcontent for the latest availability information and additional product content details.

TBD: The Pb-Free/Green conversion plan has not been defined.

Pb-Free (RoHS): TI's terms "Lead-Free" or "Pb-Free" mean semiconductor products that are compatible with the current RoHS requirements for all 6 substances, including the requirement that lead not exceed 0.1% by weight in homogeneous materials. Where designed to be soldered at high temperatures, TI Pb-Free products are suitable for use in specified lead-free processes. **Pb-Free** (RoHS Exempt): This component has a RoHS exemption for either 1) lead-based flip-chip solder bumps used between the die and package, or 2) lead-based die adhesive used between the die and leadframe. The component is otherwise considered Pb-Free (RoHS compatible) as defined above.

Green (RoHS & no Sb/Br): TI defines "Green" to mean Pb-Free (RoHS compatible), and free of Bromine (Br) and Antimony (Sb) based flame retardants (Br or Sb do not exceed 0.1% by weight in homogeneous material)

- (3) MSL, Peak Temp. The Moisture Sensitivity Level rating according to the JEDEC industry standard classifications, and peak solder temperature.
- (4) There may be additional marking, which relates to the logo, the lot trace code information, or the environmental category on the device.
- (5) Multiple Device Markings will be inside parentheses. Only one Device Marking contained in parentheses and separated by a "~" will appear on a device. If a line is indented then it is a continuation of the previous line and the two combined represent the entire Device Marking for that device.
- (6) Lead/Ball Finish Orderable Devices may have multiple material finish options. Finish options are separated by a vertical ruled line. Lead/Ball Finish values may wrap to two lines if the finish value exceeds the maximum column width.



PACKAGE OPTION ADDENDUM

16-Feb-2016

Important Information and Disclaimer: The information provided on this page represents TI's knowledge and belief as of the date that it is provided. TI bases its knowledge and belief on information provided by third parties, and makes no representation or warranty as to the accuracy of such information. Efforts are underway to better integrate information from third parties. TI has taken and continues to take reasonable steps to provide representative and accurate information but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals. TI and TI suppliers consider certain information to be proprietary, and thus CAS numbers and other limited information may not be available for release.

In no event shall TI's liability arising out of such information exceed the total purchase price of the TI part(s) at issue in this document sold by TI to Customer on an annual basis.

PACKAGE MATERIALS INFORMATION

www.ti.com 16-Feb-2016

TAPE AND REEL INFORMATION





	Dimension designed to accommodate the component width
	Dimension designed to accommodate the component length
K0	Dimension designed to accommodate the component thickness
W	Overall width of the carrier tape
P1	Pitch between successive cavity centers

QUADRANT ASSIGNMENTS FOR PIN 1 ORIENTATION IN TAPE



*All dimensions are nominal


Device	Package Type	Package Drawing	Pins	SPQ	Reel Diameter (mm)	Reel Width W1 (mm)	A0 (mm)	B0 (mm)	K0 (mm)	P1 (mm)	W (mm)	Pin1 Quadrant
LM2670SD-12/NOPB	VSON	NHM	14	250	178.0	16.4	5.3	6.3	1.5	12.0	16.0	Q1
LM2670SD-3.3/NOPB	VSON	NHM	14	250	178.0	16.4	5.3	6.3	1.5	12.0	16.0	Q1
LM2670SD-5.0/NOPB	VSON	NHM	14	250	178.0	16.4	5.3	6.3	1.5	12.0	16.0	Q1
LM2670SD-ADJ/NOPB	VSON	NHM	14	250	178.0	16.4	5.3	6.3	1.5	12.0	16.0	Q1
LM2670SDX-3.3/NOPB	VSON	NHM	14	2500	330.0	16.4	5.3	6.3	1.5	12.0	16.0	Q1
LM2670SDX-5.0/NOPB	VSON	NHM	14	2500	330.0	16.4	5.3	6.3	1.5	12.0	16.0	Q1
LM2670SDX-ADJ/NOPB	VSON	NHM	14	2500	330.0	16.4	5.3	6.3	1.5	12.0	16.0	Q1
LM2670SX-12/NOPB	DDPAK/ TO-263	KTW	7	500	330.0	24.4	10.75	14.85	5.0	16.0	24.0	Q2
LM2670SX-3.3/NOPB	DDPAK/ TO-263	KTW	7	500	330.0	24.4	10.75	14.85	5.0	16.0	24.0	Q2
LM2670SX-5.0/NOPB	DDPAK/ TO-263	KTW	7	500	330.0	24.4	10.75	14.85	5.0	16.0	24.0	Q2
LM2670SX-ADJ	DDPAK/ TO-263	KTW	7	500	330.0	24.4	10.75	14.85	5.0	16.0	24.0	Q2
LM2670SX-ADJ/NOPB	DDPAK/ TO-263	KTW	7	500	330.0	24.4	10.75	14.85	5.0	16.0	24.0	Q2

www.ti.com 16-Feb-2016




*All dimensions are nominal


Device	Package Type	Package Drawing	Pins	SPQ	Length (mm)	Width (mm)	Height (mm)
LM2670SD-12/NOPB	VSON	NHM	14	250	210.0	185.0	35.0
LM2670SD-3.3/NOPB	VSON	NHM	14	250	210.0	185.0	35.0
LM2670SD-5.0/NOPB	VSON	NHM	14	250	210.0	185.0	35.0
LM2670SD-ADJ/NOPB	VSON	NHM	14	250	210.0	185.0	35.0
LM2670SDX-3.3/NOPB	VSON	NHM	14	2500	367.0	367.0	35.0
LM2670SDX-5.0/NOPB	VSON	NHM	14	2500	367.0	367.0	35.0
LM2670SDX-ADJ/NOPB	VSON	NHM	14	2500	367.0	367.0	35.0
LM2670SX-12/NOPB	DDPAK/TO-263	KTW	7	500	367.0	367.0	45.0
LM2670SX-3.3/NOPB	DDPAK/TO-263	KTW	7	500	367.0	367.0	45.0
LM2670SX-5.0/NOPB	DDPAK/TO-263	KTW	7	500	367.0	367.0	45.0
LM2670SX-ADJ	DDPAK/TO-263	KTW	7	500	367.0	367.0	45.0
LM2670SX-ADJ/NOPB	DDPAK/TO-263	KTW	7	500	367.0	367.0	45.0











IMPORTANT NOTICE

Texas Instruments Incorporated and its subsidiaries (TI) reserve the right to make corrections, enhancements, improvements and other changes to its semiconductor products and services per JESD46, latest issue, and to discontinue any product or service per JESD48, latest issue. Buyers should obtain the latest relevant information before placing orders and should verify that such information is current and complete. All semiconductor products (also referred to herein as "components") are sold subject to TI's terms and conditions of sale supplied at the time of order acknowledgment.

TI warrants performance of its components to the specifications applicable at the time of sale, in accordance with the warranty in TI's terms and conditions of sale of semiconductor products. Testing and other quality control techniques are used to the extent TI deems necessary to support this warranty. Except where mandated by applicable law, testing of all parameters of each component is not necessarily performed.

TI assumes no liability for applications assistance or the design of Buyers' products. Buyers are responsible for their products and applications using TI components. To minimize the risks associated with Buyers' products and applications, Buyers should provide adequate design and operating safeguards.

TI does not warrant or represent that any license, either express or implied, is granted under any patent right, copyright, mask work right, or other intellectual property right relating to any combination, machine, or process in which TI components or services are used. Information published by TI regarding third-party products or services does not constitute a license to use such products or services or a warranty or endorsement thereof. Use of such information may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

Reproduction of significant portions of TI information in TI data books or data sheets is permissible only if reproduction is without alteration and is accompanied by all associated warranties, conditions, limitations, and notices. TI is not responsible or liable for such altered documentation. Information of third parties may be subject to additional restrictions.

Resale of TI components or services with statements different from or beyond the parameters stated by TI for that component or service voids all express and any implied warranties for the associated TI component or service and is an unfair and deceptive business practice. TI is not responsible or liable for any such statements.

Buyer acknowledges and agrees that it is solely responsible for compliance with all legal, regulatory and safety-related requirements concerning its products, and any use of TI components in its applications, notwithstanding any applications-related information or support that may be provided by TI. Buyer represents and agrees that it has all the necessary expertise to create and implement safeguards which anticipate dangerous consequences of failures, monitor failures and their consequences, lessen the likelihood of failures that might cause harm and take appropriate remedial actions. Buyer will fully indemnify TI and its representatives against any damages arising out of the use of any TI components in safety-critical applications.

In some cases, TI components may be promoted specifically to facilitate safety-related applications. With such components, TI's goal is to help enable customers to design and create their own end-product solutions that meet applicable functional safety standards and requirements. Nonetheless, such components are subject to these terms.

No TI components are authorized for use in FDA Class III (or similar life-critical medical equipment) unless authorized officers of the parties have executed a special agreement specifically governing such use.

Only those TI components which TI has specifically designated as military grade or "enhanced plastic" are designed and intended for use in military/aerospace applications or environments. Buyer acknowledges and agrees that any military or aerospace use of TI components which have *not* been so designated is solely at the Buyer's risk, and that Buyer is solely responsible for compliance with all legal and regulatory requirements in connection with such use.

TI has specifically designated certain components as meeting ISO/TS16949 requirements, mainly for automotive use. In any case of use of non-designated products, TI will not be responsible for any failure to meet ISO/TS16949.

Products Applications

Audio www.ti.com/audio Automotive and Transportation www.ti.com/automotive **Amplifiers** amplifier.ti.com Communications and Telecom www.ti.com/communications **Data Converters** dataconverter.ti.com Computers and Peripherals www.ti.com/computers **DLP® Products** www.dlp.com Consumer Electronics www.ti.com/consumer-apps DSP dsp.ti.com **Energy and Lighting** www.ti.com/energy Clocks and Timers www.ti.com/clocks Industrial www.ti.com/industrial Interface interface.ti.com Medical www.ti.com/medical Logic Security www.ti.com/security logic.ti.com

Power Mgmt power.ti.com Space, Avionics and Defense www.ti.com/space-avionics-defense

Microcontrollers microcontroller.ti.com Video and Imaging www.ti.com/video

RFID www.ti-rfid.com

OMAP Applications Processors www.ti.com/omap TI E2E Community e2e.ti.com

Wireless Connectivity www.ti.com/wirelessconnectivity