Notice for TAIYO YUDEN products

Please read this notice before using the TAIYO YUDEN products.

REMINDERS

Product Information in this Catalog

Product information in this catalog is as of January 2021. All of the contents specified herein and production status of the products listed in this catalog are subject to change without notice due to technical improvement of our products, etc. Therefore, please check for the latest information carefully before practical application or use of our products.

Please note that TAIYO YUDEN shall not be in any way responsible for any damages and defects in products or equipment incorporating our products, which are caused under the conditions other than those specified in this catalog or individual product specification sheets.

Approval of Product Specifications

Please contact TAIYO YUDEN for further details of product specifications as the individual product specification sheets are available. When using our products, please be sure to approve our product specifications or make a written agreement on the product specification with TAIYO YUDEN in advance.

Pre-Evaluation in the Actual Equipment and Conditions

Please conduct validation and verification of our products in actual conditions of mounting and operating environment before using our products.

Limited Application

1. Equipment Intended for Use

The products listed in this catalog are intended for generalpurpose and standard use in general electronic equipment (e.g., AV equipment, OA equipment, home electric appliances, office equipment, information and communication equipment including, without limitation, mobile phone, and PC) and other equipment specified in this catalog or the individual product specification sheets.

TAIYO YUDEN has the line-up of the products intended for use in automotive electronic equipment, telecommunications infrastructure and industrial equipment, or medical devices classified as GHTF Classes A to C (Japan Classes I to III). Therefore, when using our products for these equipment, please check available applications specified in this catalog or the individual product specification sheets and use the corresponding products.

2. Equipment Requiring Inquiry

Please be sure to contact TAIYO YUDEN for further information before using the products listed in this catalog for the following equipment (excluding intended equipment as specified in this catalog or the individual product specification sheets) which may cause loss of human life, bodily injury, serious property damage and/or serious public impact due to a failure or defect of the products and/or malfunction attributed thereto.

- (1) Transportation equipment (automotive powertrain control system, train control system, and ship control system, etc.)
- (2) Traffic signal equipment
- (3) Disaster prevention equipment, crime prevention equipment
- (4) Medical devices classified as GHTF Class C (Japan Class III)
- (5) Highly public information network equipment, dataprocessing equipment (telephone exchange, and base station, etc.)
- (6) Any other equipment requiring high levels of quality and/or reliability equal to the equipment listed above

3. Equipment Prohibited for Use

Please do not incorporate our products into the following equipment requiring extremely high levels of safety and/or reliability.

- (1) Aerospace equipment (artificial satellite, rocket, etc.)
- (2) Aviation equipment *1
- (3) Medical devices classified as GHTF Class D (Japan Class IV), implantable medical devices *²

- (4) Power generation control equipment (nuclear power, hydroelectric power, thermal power plant control system, etc.)
- (5) Undersea equipment (submarine repeating equipment, underwater work equipment, etc.)
- (6) Military equipment
- Any other equipment requiring extremely high levels of safety and/or reliability equal to the equipment listed above

*Notes:

- There is a possibility that our products can be used only for aviation equipment that does not directly affect the safe operation of aircraft (e.g., in-flight entertainment, cabin light, electric seat, cooking equipment) if such use meets requirements specified separately by TAIYO YUDEN. Please be sure to contact TAIYO YUDEN for further information before using our products for such aviation equipment.
- Implantable medical devices contain not only internal unit which is implanted in a body, but also external unit which is connected to the internal unit.

4. Limitation of Liability

Please note that unless you obtain prior written consent of TAIYO YUDEN, TAIYO YUDEN shall not be in any way responsible for any damages incurred by you or third parties arising from use of the products listed in this catalog for any equipment that is not intended for use by TAIYO YUDEN, or any equipment requiring inquiry to TAIYO YUDEN or prohibited for use by TAIYO YUDEN as described above.

Safety Design

When using our products for high safety and/or reliability-required equipment or circuits, please fully perform safety and/or reliability evaluation. In addition, please install (i) systems equipped with a protection circuit and a protection device and/or (ii) systems equipped with a redundant circuit or other system to prevent an unsafe status in the event of a single fault for a failsafe design to ensure safety.

Intellectual Property Rights

Information contained in this catalog is intended to convey examples of typical performances and/or applications of our products and is not intended to make any warranty with respect to the intellectual property rights or any other related rights of TAIYO YUDEN or any third parties nor grant any license under such rights.

Limited Warranty

Please note that the scope of warranty for our products is limited to the delivered our products themselves and TAIYO YUDEN shall not be in any way responsible for any damages resulting from a failure or defect in our products. Notwithstanding the foregoing, if there is a written agreement (e.g., supply and purchase agreement, quality assurance agreement) signed by TAIYO YUDEN and your company, TAIYO YUDEN will warrant our products in accordance with such agreement.

TAIYO YUDEN's Official Sales Channel

The contents of this catalog are applicable to our products which are purchased from our sales offices or authorized distributors (hereinafter "TAIYO YUDEN's official sales channel"). Please note that the contents of this catalog are not applicable to our products purchased from any seller other than TAIYO YUDEN's official sales channel.

Caution for Export

Some of our products listed in this catalog may require specific procedures for export according to "U.S. Export Administration Regulations", "Foreign Exchange and Foreign Trade Control Law" of Japan, and other applicable regulations. Should you have any questions on this matter, please contact our sales staff.

Automotive Application Guide

We classify automotive electronic equipment into the following four application categories and set usable application categories for each of our products. When using our products for automotive electronic equipment, please be sure to check such application categories and use our products accordingly. Should you have any questions on this matter, please contact us.

Category	Automotive Electronic Equipment (Typical Example)		
POWERTRAIN	 Engine ECU (Electronically Controlled Fuel Injector) Cruise Control Unit 4WS (4 Wheel Steering) Transmission Power Steering HEV/PHV/EV Core Control (Battery, Inverter, DC-DC) Automotive Locator (Car location information providing device), etc. 		
SAFETY	 ABS (Anti-Lock Brake System) ESC (Electronic Stability Control) Airbag ADAS (Equipment that directly controls running, turning and stopping), etc. 		
BODY & CHASSIS	 Wiper Automatic Door Power Window Keyless Entry System Electric Door Mirror Automobile Digital Mirror Interior Lighting Automobile Air Conditioning System LED Headlight TPMS (Tire Pressure Monitoring System) Anti-Theft Device (Immobilizer), etc. 		
INFOTAINMENT	 Car Infotainment System ITS/Telematics System Instrument Cluster ADAS (Sensor, Equipment that is not interlocked with safety equipment or powertrain) Dashcam (genuine products for automotive manufacturer), etc. 		

MULTILAYER CERAMIC CAPACITORS



PART NUMBER

MK 3 6 ΔB J 1 0 6 M L H T 🛆 J 1 5 (8) 9 (10) (12) 2 (4) $\overline{\mathcal{O}}$ (11) 1 3 6

①Rated voltage

Code	Rated voltage[VDC]
А	4
J	6.3
L	10
E	16
Т	25
G	35
U	50
Н	100
Q	250
S	630

②Series name

E Controo Harrio			
Code	Series name		
М	Multilayer ceramic capacitor		
V	Multilayer ceramic capacitor for high frequency		
W	LW reverse type multilayer capacitor		

 $\Delta =$ Blank space

③End terminatio	n			
Code	End termination			
К	Plated			
J	Soft Termination			
S	Cu Internal Electrodes (For High Frequency)			
F	High Reliability Application			
R	High Reliability Application			
	(Cu External Electrodes)			

(4)Dimension (L × W)

Туре	Dimensions (L×W)[mm]	EIA (inch)
063	0.6 × 0.3	0201
105	1.0 × 0.5	0402
105	0.52×1.0 💥	0204
107	1.6 × 0.8	0603
	0.8 × 1.6 💥	0306
010	2.0 × 1.25	0805
212	1.25×2.0 💥	0508
316	3.2 × 1.6	1206
325	3.2 × 2.5	1210
432	4.5 × 3.2	1812

type(r)

ode	Туре	L[mm]	W[mm]	T[mm]
Δ	ALL	Standard	Standard	Standard
C	063	0.6±0.05	0.3±0.05	0.3±0.05
	105	1.0±0.10	0.5±0.10	0.5±0.10
	107	1.6+0.15/-0.05	0.8+0.15/-0.05	0.8+0.15/-0.05
A	010	201015/ 005	1.05 0.15 / 0.05	0.85±0.10
	212	2.0+0.15/-0.05	1.25+0.15/-0.05	1.25+0.15/-0.05
	316	3.2±0.20	1.6±0.20	1.6±0.20
	325	3.2±0.30	2.5±0.30	2.5±0.30
	105	1.0+0.15/-0.05	0.5+0.15/-0.05	0.5+0.15/-0.05
	107	1.6+0.20/-0	0.8+0.20/-0	0.8+0.20/-0
В	212	2.0+0.20/-0	1.25+0.20/-0	0.85±0.10
	212	2.0+0.20/-0	1.23 1 0.20/ 0	1.25+0.20/-0
	316	3.2±0.30	1.6±0.30	1.6±0.30
	105	1.0+0.20/-0	0.5+0.20/-0	0.5+0.20/-0
С	107	1.6+0.25/-0	0.8+0.25/-0	0.8+0.25/-0
	212	2.0+0.25/-0	1.25+0.25/-0	1.25+0.25/-0
	212	2.0±0.15	1.25±0.15	0.85 ± 0.15
	316	010 0.0 0.00	16+020	1.15±0.20
К	310	3.2 ± 0.20	1.6±0.20	1.6±0.20
	325	3.2±0.50	2.5±0.30	2.5±0.30

Note: cf. STANDARD EXTERNAL DIMENSIONS

 Δ = Blank space

6 Temperature characteristics code

High dielectric	type						
Code		cable Idard	Temperature range[°C]	Ref. Temp.[°C]	Capacitance change	Capacitance tolerance	Tolerance code
BJ	EIA	X5R	$-55 \sim + 85$	25	±15%	±10%	К
БЈ	EIA	AJK	-00/0 + 00	25	±13%	±20%	М
C6	EIA	X6S	$-55 \sim +105$	25	±22%	±10%	К
00	EIA	703	-55/- +105	25	1 22 %	±20%	М
B7	EIA	X7R	$-55 \sim +125$	25	±15%	±10%	К
D7	EIA	A/K	-55/- +125	25	±13%	±20%	М
C7	EIA	X7S	$-55 \sim +125$	25	±22%	±10%	К
07	EIA	~/3	-55/- +125	20	<u> </u>	±20%	М
D7	EIA	Х7Т	$-55 \sim +125$	25	+ 2204 / - 2204	±10%	К
07	EIA	~/1	-55-9 + 125	20	+22%/-33%	±20%	М

Temperature compensating type

Temperature d	ompensa	ating type	3						
Code		cable dard	Temperature range[°C]	Ref. Temp.[°C]	Capacitance change	Capacitance tolerance	Tolerance code		
					±0.1pF	В			
JIS (IS CG	G	20		±0.25pF	С			
CG		55 a. 195 0+20 arm /°C			$-55 \sim +125$	55 ct + 125	0±30ppm/°C	$\pm 0.5 pF$	D
Ga	CG -55~+125		0±30ppm/ C	±1pF	F				
E	EIA	EIA COG	A COG	25		±2%	G		
						±5%	J		

ONominal capacitance

Code (example)	Nominal capacitance			
0R5	0.5pF			
010	1pF			
100	10pF			
101	100pF			
102	1,000pF			
103	0.01 µ F			
104	0.1 <i>µ</i> F			
105	1.0 <i>µ</i> F			
106	10 µ F			
107	100 µ F			

Note : R=Decimal point

Or Beneficial State S				
Code	Capacitance tolerance			
А	±0.05pF			
В	±0.1pF			
С	±0.25pF			
D	±0.5pF			
G	±2%			
J	±5%			
К	±10%			
М	±20%			

(9)Thickness	
Code	Thickness[mm]
Р	0.3
Т	0.3
V	0.5
С	0.7(107type or more)
A	0.8
D	0.85(212type or more)
F	1.15
G	1.25
L	1.6
Ν	1.9
М	2.5

①Special	code
----------	------

Code	Special code
-	Standard
Н	MLCC for Automotive
8	MLCC for Telecommunications infrastructure and Industrial equipment / Medical devices

①Packaging


0	
Code	Packaging
F	ϕ 178mm Taping (2mm pitch)
R	ϕ 178mm Embossed Taping (4mm pitch)
Т	ϕ 178mm Taping (4mm pitch)
	ϕ 178mm Taping (4mm pitch, 1000 pcs/reel)
P	325 type(Thickness code M)


12 Internal cod

Winternal code	
Code	Internal code
Δ	Standard

This catalog contains the typical specification only due to the limitation of space. When you consider the purchase of our products, please check our product specification sheets. For details of each product (characteristics graph, reliability information, precautions for use, and so on), see our website (http://www.ty-top.com/).

For Automotive Electronic Equipment MULTILAYER CERAMIC CAPACITORS





※ LW reverse type

		Dime	nsion [mm] (inch)			
Type(EIA)	L	W	Т	*1	е	
□MK063(0201)	0.6 ± 0.03 (0.024 \pm 0.001)	0.3 ± 0.03 (0.012 \pm 0.001)	0.3±0.03 (0.012±0.001)	т	0.15 ± 0.05 (0.006 \pm 0.002)	
□MK105(0402) □MF105(0402)	1.0 ± 0.05 (0.039 \pm 0.002)	0.5 ± 0.05 (0.020 ± 0.002)	0.5 ± 0.05 (0.020 ± 0.002)	V	0.25 ± 0.10 (0.010 ± 0.004)	
□WK105(0204)※	0.52 ± 0.05 (0.020 ± 0.002)	1.0 ± 0.05 (0.039 ± 0.002)	0.3 ± 0.05 (0.012 \pm 0.002)	Р	0.18 ± 0.08 (0.007 ± 0.003)	
□MK107(0603) □MF107(0603)	1.6 ± 0.10 (0.063 ± 0.004)	0.8 ± 0.10 (0.031 ± 0.004)	0.8±0.10 (0.031±0.004)	А	0.35 ± 0.25 (0.014 ± 0.010)	
□MJ107(0603)	1.6 ± 0.10 (0.063 ± 0.004)	0.8 ± 0.10 (0.031 ± 0.004)	0.8±0.10 (0.031±0.004)	А	0.35+0.3/-0.25 (0.014+0.012/-0.010)	
□VS107(0603)	1.6 ± 0.10 (0.063 ± 0.004)	0.8 ± 0.10 (0.031 ± 0.004)	0.7±0.10 (0.028±0.004)	С	0.35±0.25 (0.014±0.010)	
□WK107(0306)※	0.8±0.10 (0.031±0.004)	1.6 ± 0.10 (0.063 ± 0.004)	0.5±0.05 (0.020±0.002)	V	0.25±0.15 (0.010±0.006)	
□MK212(0805)	2.0±0.10	1.25±0.10	0.85±0.10 (0.033±0.004)	D	0.5±0.25	
□MF212(0805)	(0.079±0.004)	(0.049±0.004)	1.25 ± 0.10 (0.049 ± 0.004)	G	(0.020±0.010)	
	2.0±0.10	0.85±0.10 1.25±0.10 (0.033±0.004)		D	0.5+0.35/-0.25	
□MJ212(0805)	(0.079 ± 0.004)	(0.049±0.004)	1.25 ± 0.10 (0.049 ± 0.004)	G	(0.020+0.014/-0.010)	
□VS212(0805)	2.0±0.10 (0.079±0.004)	1.25 ± 0.10 (0.049 ± 0.004)	0.85±0.10 (0.033±0.004)	D	0.5±0.25 (0.020±0.010)	
□WK212(0508)※	1.25±0.15 (0.049±0.006)	2.0±0.15 (0.079±0.006)	0.85±0.10 (0.033±0.004)	D	0.3±0.2 (0.012±0.008)	
□MK316(1206)	3.2±0.15	1.6±0.15	1.15±0.10 (0.045±0.004)	F	0.5+0.35/-0.25	
□MF316(1206)	(0.126±0.006)	(0.063±0.006)	1.6 ± 0.20 (0.063 ± 0.008)	L	(0.020+0.014/-0.010)	
	3.2±0.15	1.6±0.15	1.15 ± 0.10 (0.045 ± 0.004)	F	0.6+0.4/-0.3	
□MJ316(1206)	(0.126±0.006)	(0.063 ± 0.006)	1.6 ± 0.20 (0.063 ± 0.008)	L	(0.024+0.016/-0.012)	
			1.15 ± 0.10 (0.045 ± 0.004)	F		
□MK325(1210) □MF325(1210)	3.2±0.30 (0.126±0.012)	2.5±0.20 (0.098±0.008)	1.9±0.20 (0.075±0.008)	N	0.6±0.3 (0.024±0.012)	
			2.5±0.20 (0.098±0.008)	М		
	3.2±0.30	2.5±0.20	1.9±0.20 (0.075±0.008)	Ν	0.6+0.4/-0.3	
□MJ325(1210)	(0.126±0.012)	(0.098±0.008)	2.5±0.20 (0.098±0.008)	М	(0.024+0.016/-0.012)	
□MK432(1812)	4.5±0.40 (0.177±0.016)	3.2 ± 0.30 (0.126 ± 0.012)	2.5 ± 0.20 (0.098 ± 0.008)	м	0.9 ± 0.6 (0.035 \pm 0.024)	

STANDARD QUANTITY

Turne	EIA (inch)	Dime	nsion	Standard qu	antity[pcs]
Туре	EIA (Inch)	[mm]	Code	Paper tape	Embossed tape
063	0201	0.3	Т	15000	-
105	0402	0.5	V	10000	
105	0204 💥	0.30	Р	10000	_
		0.7	С	4000	
		0.8	А	4000	_
107	0603	0.8	А	3000 (Soft Termination)	-
		0.8	А	-	3000 (Soft Termination
	0306 💥	0.50	V	-	4000
		0.85	D	4000	_
	0805	1.25	G	-	3000
212	0805	1.25	G	_	2000 (Soft Termination
	0508 💥	0.85	D	4000	-
316	1206	1.15	F	-	3000
310	1200	1.6	L	-	2000
		1.15	F		2000
325	1210	1.9	Ν		2000
		2.5	М	-	500(T), 1000(P)
432	1812	2.5	М	_	500

AUTO

Medium-High Voltage Multilaver Ceramic Capacitors

• 105TYPE (Demension:1.0 × 0.5mm JIS:1005 EIA:0402)

[Temperature Characteristic B7 : X7R(-55~+125°C), C7 : X7S(-55~+125°C)] 0.5mm thickness(V)

Part number 1	Part number 2	Rated voltage	Tempe	erature	Capacitance	Capacitance	tan δ	HTLT	Thickness ^{*1} [mm]	Note
Part number 1	Part number 2	[V]	charact	eristics	[F]	tolerance [%]	[%]	Rated voltage x %	Inickness [mm]	Note
HMK105 B7221 VHFE				X7R	220 p	±10, ±20	3.5	200	0.5 ± 0.05	
HMK105 B7331[]VHFE				X7R	330 p	±10, ±20	3.5	200	0.5 ± 0.05	
HMK105 B7471 VHFE				X7R	470 p	±10, ±20	3.5	200	0.5 ± 0.05	
HMK105 B7681[]VHFE				X7R	680 p	±10, ±20	3.5	200	0.5 ± 0.05	
HMK105 B7102[]VHFE				X7R	1000 p	±10, ±20	3.5	200	0.5 ± 0.05	
HMK105 B7152[]VHFE		100		X7R	1500 p	±10, ±20	3.5	200	0.5 ± 0.05	
HMK105 B7222[]VHFE				X7R	2200 p	±10, ±20	3.5	200	0.5 ± 0.05	
HMK105 B7332[]VHFE				X7R	3300 p	±10, ±20	3.5	200	0.5 ± 0.05	
HMK105 B7472[]VHFE				X7R	4700 p	±10, ±20	3.5	200	0.5 ± 0.05	
HMK105 B7682[]VHFE				X7R	6800 p	±10, ±20	3.5	200	0.5 ± 0.05	
HMK105 B7103 VHFE				X7R	0.01 µ	±10, ±20	3.5	200	0.5 ± 0.05	

107TYPE (Dimension:1.6 × 0.8mm JIS:1608 EIA:0603)

[Temperature Characteristic B7 : $X7R(-55 \sim +125^{\circ}C)$, C7 : $X7S(-55 \sim +125^{\circ}C)$] 0.8mm thickness(A)

Part number 1	Part number 2	Rated voltage	Temperature		Capacitance tolerance [%]	tan δ	HTLT	Thickness ^{*1} [mm]	Note
		[V]	characteristics	characteristics [F]		[%]	Rated voltage x %	THIS REAL PROPERTY IN THE PROPERTY INTERPOPERTY IN THE PROPERTY INTERPOPERTY INTERPOPE	
HMK107 B7102[]AHT			X7R	1000 p	±10, ±20	3.5	200	0.8±0.10	
HMK107 B7152[]AHT			X7R	1500 p	±10, ±20	3.5	200	0.8±0.10	
HMK107 B7222[]AHT			X7R	2200 p	±10, ±20	3.5	200	0.8±0.10	
HMK107 B7332[]AHT			X7R	3300 p	±10, ±20	3.5	200	0.8±0.10	
HMK107 B7472[]AHT			X7R	4700 p	±10, ±20	3.5	200	0.8±0.10	
HMK107 B7682[]AHT			X7R	6800 p	±10, ±20	3.5	200	0.8±0.10	
HMK107 B7103[]AHT			X7R	0.01 µ	±10, ±20	3.5	200	0.8±0.10	
HMK107 B7153[]AHT		100	X7R	0.015 µ	±10, ±20	3.5	200	0.8±0.10	
HMK107 B7223[]AHT			X7R	0.022 µ	±10, ±20	3.5	200	0.8±0.10	
HMK107 B7333[]AHT			X7R	0.033 µ	±10, ±20	3.5	200	0.8±0.10	
HMK107 B7473[AHT			X7R	0.047 μ	±10, ±20	3.5	200	0.8±0.10	
HMK107AB7683[]AHTE			X7R	0.068 µ	±10, ±20	3.5	200	0.8+0.15/-0.05	
HMK107 B7104[]AHT		-	X7R	0.1 μ	±10, ±20	3.5	200	0.8±0.10	
HMK107AC7154[]AHTE			X7S	0.15 μ	±10, ±20	3.5	150	0.8+0.15/-0.05	
HMK107 C7224[]AHTE			X7S	0.22 μ	±10, ±20	3.5	150	0.8±0.10	

212TYPE (Dimension:2.0 × 1.25mm JIS:2012 EIA:0805)

[Temperature Characteristic B7 : $X7R(-55 \sim + 125^{\circ}C)$, C7 : $X7S(-55 \sim + 125^{\circ}C)$] 1.25mm thickness(G)

Part number 1	Deut wurdt au 0	Rated voltage	Tempe	erature	Capacitance	Capacitance	tan δ	HTLT	Thickness ^{*1} [mm]	Note
Part number 1	Part number 2	[V]	characteristics		[F]	tolerance [%]	[%]	Rated voltage x %	Inickness [mm]	Note
HMK212 B7472[]GHT				X7R	4700 p	±10, ±20	2.5	200	1.25±0.10	
HMK212 B7682[]GHT				X7R	6800 p	±10, ±20	2.5	200	1.25 ± 0.10	
HMK212 B7103[]GHT				X7R	0.01 µ	±10, ±20	3.5	200	1.25 ± 0.10	
HMK212 B7153[]GHT				X7R	0.015 μ	±10, ±20	3.5	200	1.25 ± 0.10	
HMK212 B7223[]GHT				X7R	0.022 µ	±10, ±20	3.5	200	1.25±0.10	
HMK212 B7333[]GHT				X7R	0.033 µ	±10, ±20	3.5	200	1.25±0.10	
HMK212 B7473[]GHT				X7R	0.047 μ	±10, ±20	3.5	200	1.25±0.10	
HMK212 B7683[]GHT		100		X7R	0.068 µ	±10, ±20	3.5	200	1.25 ± 0.10	
HMK212 B7104[]GHT				X7R	0.1 μ	±10, ±20	3.5	200	1.25 ± 0.10	
HMK212BB7154[]GHTE				X7R	0.15 μ	±10, ±20	3.5	200	1.25+0.20/-0	
HMK212 B7224[]GHT				X7R	0.22 μ	±10, ±20	3.5	200	1.25 ± 0.10	
HMK212BC7334[]GHTE				X7S	0.33 μ	±10, ±20	3.5	150	1.25+0.20/-0	
HMK212 C7474[]GHTE				X7S	0.47 μ	±10, ±20	3.5	150	1.25 ± 0.10	
HMK212CC7684[]GHTE				X7S	0.68 µ	±10, ±20	3.5	150	1.25+0.25/-0	
HMK212BC7105[]GHTE				X7S	1 μ	±10, ±20	3.5	150	1.25+0.20/-0	
QMK212 B7472[]GHT				X7R	4700 p	±10, ±20	2.5	150	1.25±0.10	
QMK212 B7682[]GHT]		X7R	6800 p	±10, ±20	2.5	150	1.25±0.10	
QMK212 B7103[]GHT		250		X7R	0.01 µ	±10, ±20	2.5	150	1.25±0.10	
QMK212 B7153[]GHT]		X7R	0.015 μ	±10, ±20	2.5	150	1.25±0.10	
QMK212 B7223 GHT]		X7R	0.022 µ	±10, ±20	2.5	150	1.25±0.10	

[Temperature Characteristic B7 : $X7R(-55 \sim +125^{\circ}C)$] 0.85mm thickness(D)

Part number 1 Part number 2		Rated voltage	Temperature		Capacitance	Capacitance	tan δ	HTLT	Thickness ^{*1} [mm]	Note
	Fart number 2	[V]	characteristics		[F]	tolerance [%]	[%]	Rated voltage x %	Inickness [mm]	Note
HMK212 B7102[]DHT				X7R	1000 p	±10, ±20	2.5	200	0.85±0.10	
HMK212 B7152[]DHT		100		X7R	1500 p	±10, ±20	2.5	200	0.85±0.10	
HMK212 B7222[]DHT		100		X7R	2200 p	±10, ±20	2.5	200	0.85±0.10	
HMK212 B7332[]DHT				X7R	3300 p	±10, ±20	2.5	200	0.85±0.10	
QMK212 B7102[]DHT				X7R	1000 p	±10, ±20	2.5	150	0.85±0.10	
QMK212 B7152[]DHT		250		X7R	1500 p	±10, ±20	2.5	150	0.85±0.10	
QMK212 B7222 DHT		250		X7R	2200 p	±10, ±20	2.5	150	0.85±0.10	
QMK212 B7332[]DHT				X7R	3300 p	±10, ±20	2.5	150	0.85±0.10	

CERAMIC CAPACITORS

PART NUMBER

316TYPE (Dimension:3.2 × 1.6mm JIS:3216 EIA:1206)

[Temperature Characteristic B7 : $X7R(-55 \sim +125^{\circ}C)$, C7 : $X7S(-55 \sim +125^{\circ}C)$] 1.6mm thickness(L)

Part number 1	Part number 2	Rated voltage	Tempe	erature	Capacitance	Capacitance	tan δ	HTLT	Thickness ^{*1} [mm]	Note
Part number i	Part number 2	[V]	charact	eristics	[F]	tolerance [%]	[%]	Rated voltage x %	Inickness [mm]	Note
HMK316 B7473[]LH	Т			X7R	0.047 μ	±10, ±20	3.5	200	1.6±0.20	
HMK316 B7683[]LH	Т			X7R	0.068 µ	±10, ±20	3.5	200	1.6±0.20	
HMK316 B7104[]LH	т			X7R	0.1 μ	±10, ±20	3.5	200	1.6±0.20	
HMK316 B7154[]LH	Т			X7R	0.15 μ	±10, ±20	3.5	200	1.6±0.20	
HMK316 B7224[]LH	Т	100		X7R	0.22 µ	±10, ±20	3.5	200	1.6±0.20	
HMK316 B7334[]LH	Т	100		X7R	0.33 µ	±10, ±20	3.5	200	1.6±0.20	
HMK316 B7474[]LH	Т			X7R	0.47 μ	±10, ±20	3.5	200	1.6±0.20	
HMK316 B7105[]LH	Т	-		X7R	1 μ	±10, ±20	3.5	200	1.6±0.20	
HMK316BC7155[LH	ITE			X7S	1.5 μ	±10, ±20	3.5	150	1.6±0.30	
HMK316AC7225[LH	ITE			X7S	2.2 μ	±10, ±20	3.5	150	1.6±0.20	
QMK316 B7223[]LH	Т			X7R	0.022 µ	±10, ±20	2.5	150	1.6±0.20	
QMK316 B7333[]LH	Т			X7R	0.033 µ	±10, ±20	2.5	150	1.6±0.20	
QMK316 B7473[]LH	Т	250		X7R	0.047 μ	±10, ±20	2.5	150	1.6±0.20	
QMK316 B7683[]LH	Т			X7R	0.068 µ	±10, ±20	2.5	150	1.6±0.20	
QMK316 B7104[]LH	Т			X7R	0.1 µ	±10, ±20	2.5	150	1.6 ± 0.20	
SMK316 B7153[]LH	Т			X7R	0.015 µ	±10, ±20	2.5	120	1.6 ± 0.20	
SMK316 B7223[]LH	Т	630		X7R	0.022 µ	±10, ±20	2.5	120	1.6±0.20	
SMK316AB7333[]LH	IT	030		X7R	0.033 µ	±10, ±20	2.5	120	1.6±0.20	
SMK316AB7473[]LH	IT]		X7R	0.047 μ	±10, ±20	2.5	120	1.6±0.20	

[Temperature Characteristic B7 : $X7R(-55 \sim +125^{\circ}C)$] 1.15mm thickness(F)

Part number 1	Part number 2	Rated voltage [V]	Temperature characteristics		Capacitance	Capacitance tolerance [%]	tan δ	HTLT	Thickness ^{*1} [mm]	Note
Part number 1	Part number 2				[F]		[%]	Rated voltage x %	Thickness [mm]	NOLO
SMK316 B7102[]FHT				X7R	1000 p	±10, ±20	2.5	120	1.15±0.10	
SMK316 B7152[]FHT				X7R	1500 p	±10, ±20	2.5	120	1.15±0.10	
SMK316 B7222[]FHT				X7R	2200 p	±10, ±20	2.5	120	1.15±0.10	
SMK316 B7332[]FHT		630		X7R	3300 p	±10, ±20	2.5	120	1.15±0.10	
SMK316 B7472[]FHT				X7R	4700 p	±10, ±20	2.5	120	1.15±0.10	
SMK316 B7682[]FHT]		X7R	6800 p	±10, ±20	2.5	120	1.15±0.10	
SMK316 B7103[]FHT				X7R	0.01 µ	±10, ±20	2.5	120	1.15±0.10	

325TYPE (Dimension:3.2 × 2.5mm JIS:3225 EIA:1210)

[Temperature Characteristic B7 : $X7R(-55 \sim +125^{\circ}C)$, C7 : $X7S(-55 \sim +125^{\circ}C)$] 2.5mm thickness(M)

Part number 1	Part number 2	Rated voltage [V]	Temperature characteristics		Capacitance [F]	Capacitance tolerance [%]	tan δ [%]	HTLT Rated voltage x %	Thickness ^{*1} [mm]	Note
HMK325 B7225[]MHP		100		X7R	2.2 μ	±10, ±20	3.5	200	2.5 ± 0.20	
HMK325 C7475 MHPE		100		X7S	4.7 μ	±10, ±20	3.5	150	2.5 ± 0.20	

[Temperature Characteristic B7 : $X7R(-55 \sim +125^{\circ}C)$] 1.9mm thickness(N)

Part number 1 Part number 2		Rated voltage	Temperature Capacitance		Capacitance	Capacitance	tan δ	HTLT	Thickness ^{*1} [mm]	Note
	[V]	characte	characteristics [tolerance [%]	[%]	Rated voltage x %	Inickness [mm]	Note	
HMK325 B7224[]NHT				X7R	0.22 µ	±10, ±20	3.5	200	1.9±0.20	
HMK325 B7474[]NHT		100		X7R	0.47 μ	±10, ±20	3.5	200	1.9 ± 0.20	
HMK325 B7684[]NHT		100		X7R	0.68 µ	±10, ±20	3.5	200	1.9 ± 0.20	
HMK325 B7105[]NHT				X7R	1 μ	±10, ±20	3.5	200	1.9±0.20	
QMK325 B7473[]NHT				X7R	0.047 μ	±10, ±20	2.5	150	1.9±0.20	
QMK325 B7104[]NHT		250		X7R	0.1 µ	±10, ±20	2.5	150	1.9±0.20	
QMK325 B7154[]NHT		230		X7R	0.15 μ	±10, ±20	2.5	150	1.9±0.20	
QMK325 B7224[]NHT				X7R	0.22 μ	±10, ±20	2.5	150	1.9±0.20	
SMK325 B7223[]NHT				X7R	0.022 µ	±10, ±20	2.5	120	1.9±0.20	
SMK325 B7333[]NHT		630		X7R	0.033 µ	±10, ±20	2.5	120	1.9±0.20	
SMK325 B7473[]NHT				X7R	0.047 μ	±10, ±20	2.5	120	1.9 ± 0.20	

432TYPE (Dimension:4.5 × 3.2mm JIS:4532 EIA:1812)

[Temperature Characteristic B7 : $X7R(-55 \sim +125^{\circ}C)$] 2.5mm thickness(M)

Part number 1	Part number 2	Rated voltage	Tempe	erature	Capacitance	Capacitance	tan δ	HTLT	Thickness ^{*1} [mm]	Note
Farthumber i	Fart number 2	[V]	charact	eristics	[F]	tolerance [%]	[%]	Rated voltage x %	Thickness [mm]	NOLE
HMK432 B7474[]MHT				X7R	0.47 μ	±10, ±20	3.5	200	2.5 ± 0.20	
HMK432 B7105[]MHT		100		X7R	1 μ	±10, ±20	3.5	200	2.5 ± 0.20	
HMK432 B7155[]MHT		100		X7R	1.5 μ	±10, ±20	3.5	200	2.5 ± 0.20	
HMK432 B7225[]MHT				X7R	2.2 μ	±10, ±20	3.5	200	2.5±0.20	
QMK432 B7104[]MHT				X7R	0.1 μ	±10, ±20	2.5	150	2.5±0.20	
QMK432 B7224[]MHT		250		X7R	0.22 μ	±10, ±20	2.5	150	2.5±0.20	
QMK432 B7334[]MHT		230		X7R	0.33 µ	±10, ±20	2.5	150	2.5±0.20	
QMK432 B7474[]MHT				X7R	0.47 μ	±10, ±20	2.5	150	2.5 ± 0.20	
SMK432 B7473[]MHT				X7R	0.047 μ	±10, ±20	2.5	120	2.5 ± 0.20	
SMK432 B7683[]MHT		630		X7R	0.068 µ	±10, ±20	2.5	120	2.5 ± 0.20	
SMK432 B7104[]MHT				X7R	0.1 μ	±10, ±20	2.5	120	2.5 ± 0.20	

Multilayer Ceramic Capacitors


PACKAGING

①Minimum Quantity

_ ()	Thick	ness	Standard o	uantity [pcs]
Type(EIA)	mm	code	Paper tape	Embossed tape
□MK021(008004)	0.105	к		50000
□VS021(008004)	0.125	n	_	50000
MK042(01005)	0.2	C, D		40000
□VS042(01005)	0.2	С		40000
□MK063(0201)	0.3	P,T	15000	—
□WK105(0204) 💥	0.3	Р	10000	_
	0.13	Н	_	20000
	0.18	E	_	15000
□MK105(0402)	0.2	С	20000	-
□MF105(0402)	0.3	Р	15000	-
	0.5	V	10000	_
□VK105(0402)	0.5	W	10000	-
MK107(0603)	0.45	К	4000	-
□WK107(0306) ※	0.5	V	-	4000
□MF107(0603)	0.8	А	4000	-
□VS107(0603)	0.7	С	4000	-
□MJ107(0603)	0.8	А	3000	3000
□MK212(0805)	0.45	К	4000	
□WK212(0508) ※	0.85	D	4000	_
□MF212(0805)	1.25	G	_	3000
□VS212(0805)	0.85	D	4000	_
	0.85	D	4000	_
□MJ212(0805)	1.25	G	-	2000
	0.85	D	4000	-
□MK316(1206)	1.15	F	_	3000
□MF316(1206)	1.6	L	-	2000
	1.15	F	-	3000
□MJ316(1206)	1.6	L	_	2000
	0.85	D		
	1.15	F		
□MK325(1210)	1.9	Ν	7 -	2000
□MF325(1210)	2.0max.	Y	1	
	2.5	М	_	1000
	1.9	Ν	—	2000
□MJ325(1210)	2.5	М	—	500(T), 1000(P)
□MK432(1812)	2.5	М	-	500


Note : 💥 LW Reverse type.

(2) Taping material




This catalog contains the typical specification only due to the limitation of space. When you consider the purchase of our products, please check our specification. For details of each product (characteristics graph, reliability information, precautions for use, and so on), see our Web site (http://www.ty-top.com/).

TAIYO YUDEN




3 Representative taping dimensions






Type(EIA)	Chip	Cavity	Insertion Pitch	Tape Thickness		
Type(EIA)	А	В	F	Т	T1	
□MK063(0201)	0.37	0.67	2.0±0.05	0.45max.	0.42max.	
□WK105(0204) ※				0.45max.	0.42max.	
□MK105(0402) (*1 C)	0.65	1.15		0.4max.	0.3max.	
□MK105(0402) (*1 P)				0.45max.	0.42max.	
Note *1 Thickness, C:0.2mm ,P:0.3mm. X LW Reverse type.					Unit:mm	



Type(EIA)	Chip (Cavity	Insertion Pitch	Tape Thickness
Type(EIA)	A	В	F	Т
□MK105 (0402) □MF105 (0402) □VK105 (0402)	0.65	1.15	2.0±0.05	0.8max.

Unit:mm







Type(EIA)	Chip (Cavity	Insertion Pitch	Tape Thickness
Type(LIA)	А	В	F	Т
□MK107(0603)				
□WK107(0306) 💥	1.0	1.8		1.1max.
□MF107(0603)			40104	
MK212(0805)	1.05	0.4	4.0±0.1	
□WK212(0508) 💥	1.65	2.4		1.1max.
DMK316(1206)	2.0	3.6		
Note:Taping size might	be different depending on	the size of the product.	※ LW Reverse type.	Unit : mm

 0.9 ± 0.05

Note: Taping size might be different depending on the size of the product. % LW Reverse type.






Type(EIA)	Chip (Cavity	Insertion Pitch	Tape Tł	nickness
Type(EIA)	А	В	F	К	Т
□MK021(008004)	0 1 2 5	0.07			
□VS021(008004)	0.135	0.27	1.0 ± 0.02	0.5max.	0.25max.
□MK042(01005)	0.00	0.40	1.0±0.02		
□VS042(01005)	0.23	0.43			

Unit:mm(inch)


Unit:mm



Type(EIA)	Chip Cavity		Chip Cavity Insertion Pitch		Insertion Pitch	Tape Thickness		
Type(EIA)	А	В	F	К	Т			
□MK105(0402)	0.6	1.1	2.0±0.1	0.6max	0.2±0.1			
□WK107(0306) ※	1.0	1.8		1.3max.	0.25 ± 0.1			
□MK212(0805)	1.65	2.4						
DMF212(0805)	1.05	2.4						
□MK316(1206)	2.0	3.6	4.0±0.1	3.4max.	0.6max.			
□MF316(1206)	2.0	3.0			0.0max.			
□MK325(1210)	2.8	3.6						
□MF325(1210)	2.0	5.0						

Note: 💥 LW Reverse type.


Unit:mm




Type(EIA)	Chip (Cavity	Insertion Pitch	Tape Tł	nickness
Type(EIA)	A	В	F	К	Т
□MK325(1210)	3.1	4.0	8.0±0.1	4.0max.	0.6max.
□MK432(1812)	3.7	4.9	8.0±0.1	4.0max.	0.6max.

Unit : mm

④Trailer and Leader




⑤Reel size



А	В	С	D	E	R
ϕ 178±2.0	<i>ф</i> 50min.	ϕ 13.0±0.2	<i>ф</i> 21.0±0.8	2.0 ± 0.5	1.0
	Т	W			
4mm wide tape	1.5max.	5±1.0			
8mm wide tape	2.5max.	10±1.5	-		
12mm wide tape	2.5max.	14±1.5	Unit : mm		

6 Top Tape Strength

The top tape requires a peel-off force of 0.1 to 0.7N in the direction of the arrow as illustrated below.





RELIABILITY DATA

1. Operating Temp	perature Range
	Temperature Compensating(High Frequency type) CG(COG) : -55 to +125°C
Specified Value	High permittivity X7R, X7S : -55 to $+125^{\circ}$ C X5 : -55 to $+85^{\circ}$ C B : -25 to $+85^{\circ}$ C

2. Storage Temper	rature Range
	Temperature Compensating(High Frequency type) CG(C0G) : -55 to $+125^{\circ}$ C
Specified Value	High permittivity X7R, X7S : -55 to $+125^{\circ}$ C X5R : -55 to $+85^{\circ}$ C B : -25 to $+85^{\circ}$ C

3. Rated Voltage	
Specified Value	100VDC(HMK,HMJ), 250VDC(QMK,QMJ,QVS), 630VDC(SMK,SMJ)

4. Withstanding Volt	age(Between terminals)	
Specified Value	No breakdown or damage	
Test Methods and Remarks	Applied voltage Duration Carge/discharge current	: Rated voltage × 2.5(HMK,HMJ), Rated voltage × 2(QMK,QMJ,QVS), Rated voltage × 1.2(SMK,SMJ) : 1 to 5sec. : 50mA max.

5. Insulation Resist	5. Insulation Resistance				
Specified Value	Temperature Compensating 10000M Ω min High permittivity 100M Ω μ F or 10G Ω , which				
Test Methods and Remarks	Applied voltage Duration Charge/discharge current	: Rated voltage(HMK,HMJ, QMK,QMJ,QVS), 500V(SMK,SMJ) : 60±5sec. : 50mA max.			

6. Capacitance (To	6. Capacitance (Tolerance)			
Specified Value	Temperature Compensating(High Frequency type) ± 0.1 pF (C ≤ 5 pF) ± 0.25 pF (C ≤ 10 pF) ± 0.5 pF (5pF $\leq C < 10$ pF) $\pm 2\%$ (C=10pF) $\pm 5\%$ (C ≥ 10 pF)			
	High permittivity			
	±10%, ±20%			
	Temperature Compensating	(High Frequency type)		
	Measuring frequency	:1MHz±10%		
	Measuring voltage	: 0.5 to 5Vrms		
Test Methods and	Bias application	: None		
Remarks	High permittivity			
	Measuring frequency	: 1kHz±10%		
	Measuring voltage	: 1±0.2Vrms		
	Bias application	: None		

7. Q or Dissipation	Factor		
	Temperature Compensating(High Frequency type)		
	C<30pF : Q≧800+20C		
	C≧30pF:Q≧1400	C:Normal Capacitance(/pF)	
Specified Value			
	High permittivity		
	3.5%max(HMK,HMJ)		
	2.5%max(QMK,QMJ, SN	(K,SMJ)	
	Temperature Compensation	ating(High Frequency type)	
	Measuring frequency	: 1MHz±10%	
	Measuring voltage	: 0.5 to 5Vrms	
Test Methods and	Bas application	: None	
Remarks			
Remarks	High permittivity		
	Measuring frequency	: 1kHz±10%	
	Measuring voltage	: 1±0.2Vrms	
	Bas application	: None	

8. Temperature Ch	aracteristic of Capacitance				
	Temperature Compensating(High Frequency type)COG:±30ppm(25 to +125°C)				
Specified Value	High permittivity B : $\pm 10\% (-25 \text{ to } +85^{\circ}\text{C})$ X5R : $\pm 15\% (-55 \text{ to } +85^{\circ}\text{C})$ X7R : $\pm 15\% (-55 \text{ to } +125^{\circ}\text{C})$ X7S : $\pm 22\% (-55 \text{ to } +125^{\circ}\text{C})$				
Test Methods and	Temperature Compensating(High Frequency type) Capacitance at 25°C and 85°C shall be measured in thermal equilibrium, and the temperature characteristic shall be calculated from the following equation. $\frac{(C_{85}-C_{25})}{C_{25} \times \Delta \Gamma} \times 10^{6} \times [ppm/^{\circ}C]$ High permittivity Capacitance value at each step shall be measured in thermal equilibrium, and the temperature characteristic shall be calculated from the following equation.				
Remarks	StepBX5R, X7R, X7S1Minimum operating tempeature220°C3Maximum operating temperature $\frac{(C-C_2)}{C_2}$ × 100(%)C: Capacitance value in Step 1 or Step 3				
	C2 : Capacitance value in Step 2				

9. Deflection	
	Temperature Compensating(High Frequency type)
	Appearance : No abnormality
	Capacitance change $\pm 5\%$ or $\pm 0.5pF$, whichever is larger.
Specified Value	
	High permittivity
	Appearance : No abnormality
	Capacitance change : Within±10%
	Warp : 1mm (Soft Termination type:3mm)
	Duration : 10sec.
	Test board : Glass epoxy-resin substrate Board R-230 Warp
Test Methods and	Thicknss : 1.6mm
Remarks	
	(Unit: mm)
	Capacitance measurement shall be conducted with the board bent.



10. Adhesive Stren	10. Adhesive Strength of Terminal Electrodes		
Specified Value	No terminal separation or its indication.		
Test Methods and Remarks	Temperature Compensating(High Frequency type) Applied force : 2N Duration : 10±1sec. High permittivity Applied force : 5N Duration : 30±5sec.		

11. Solderability			
Specified Value	At least 95% of terminal elect	rode is covered by new solder	
		Eutectic solder	Lead-free solder
Test Methods and	Solder type	H60A or H63A	Sn-3.0Ag-0.5Cu
Remarks	Solder temperature	230±5°C	245±3°C
	Duration	4±1	sec.

12. Resistance to S	Soldering		
	Temperature Compensating(High Frequency type)		
	Appearance	: No abnormality	
	Capacitance change	: C※≦10pF :±0.25pF C※>10pF :±2.5% ※Normal capacitance	
	Insulation resistance	: Initial value	
	Withstanding voltage	(between terminals) : No abnormality	
Specified Value	High permittivity		
	Appearance	: No abnormality	
	Capacitance change	: Within±15%(HMK,HMJ), ±10%(QMK,QMJ, SMK,SMJ)	
	Dissipation factor	: Inital value	
	Insulation resistance	: Initial value	
	Withstanding voltage	(between terminals) : No abnormality	
	Preconditioning : Thermal treatment (at 150°C for 1hr) Note1 (Only High permittivity)		
Test Methods and	Solder temperature	: 270±5°C	
Remarks	Duration	: 3±0.5sec.	
Remarks	Preheating conditions	: 80 to 100°C, 2 to 5 min. 150 to 200°C, 2 to 5min.	
	Recovery	: 24 \pm 2hrs under the stadard condition Note3	

13. Temperature C	13. Temperature Cycle (Thermal Shock)			
	Temperature Compensating(High Frequency type)			
	Appearance	: No abnormality		
	Capacitance change	: C※≦10pF :±0.25% C※>10pF :±	2.5%	
	Insulation resistance	: Initial value		
	Withstanding voltage	(between terminals) : No abnormality		
Specified Value	High permittivity			
	Appearance	: No abnormality		
	Capacitance change	: Within $\pm 15\%$ (HMK,HMJ), $\pm 7.5\%$ (QMK,QMJ, SMK,SMJ)		
	Dissipation factor	: Initial value		
	Insulation resistance	: Initial value		
	Withstanding voltage (between terminals) : No abnormality			
	Preconditioning : The	rmal treatment (at 150°C for 1hr) Note1		
	Conditions for 1 cycl	e		
	Step	temperature(°C)	Time(min.)	
Test Methods and	1	Minimum operating temperature	30 ± 3 min.	
Test Methods and Remarks	2	Normal temperature	2 to 3min.	
Remarks	3	Maximum operating temperature	30±3min.	
	4	Normal temperature	2 to 3min.	
	Number of cycles : 5	times		
	Recovery : 24±2hrs	under the standard condition Note3		

14. Humidity (Stea	14. Humidity (Steady state)				
	Temperature Compensati	ng(High Frequency type)			
	Appearance	: No abnormality			
	Capacitance change	: C‰≦10pF :±0.5pF C‰>10pF :±5% %Normal capacitance			
	Insulation resistance	: 1000M Ω min			
Specified Value	High permittivity				
	Appearance	: No abnormality			
	Capacitance change	: Within $\pm 15\%$			
	Dissipation factor	: 7%max(HMK,HMJ), 5%max(QMK,QMJ, SMK,SMJ).			
	Insulation resistance	: 25M Ω μ F or 1000M Ω , whichever is smaller.			
	Preconditioning	: Thermal treatment(at 150°C for 1hr) Note1 (Only High permittivity)			
Test Methods and	Temperature	: 40±2°C			
	Humidity	: 90 to 95%RH			
Remarks	Duration	: 500 +24/-0 hrs			
	Recovery	: 24 \pm 2hrs under the standard condition Note3			


15. Humidity Loadir	ng				
	Temperature Compensating(High Frequency type)				
	Appearance	: No abnormality			
	Capacitance change	:C‰≦2.0pF:±0.4pF 2.0pF <c≦10pf: c‰="" ±0.75pf="">10pF:±7.5%</c≦10pf:>			
		: XNormal capacitance			
	Insulation resistance	: 500M Ω min			
Specified Value					
	High permittivity				
	Appearance	: No abnormality			
	Capacitance change	: Within \pm 15%			
	Dissipation factor	:7%max(HMK,HMJ), 5%max(QMK,QMJ, SMK,SMJ).			
	Insulation resistance	: 10M Ω μ F or 500M Ω , whichever is smaller.			
	According to JIS 5102 clause 9.9.				
	Preconditioning	: Voltage treatment Note2 (Only High permittivity)			
	Temperature	: 40±2°C			
Test Methods and	Humidity	: 90 to 95%RH			
Remarks	Applied voltage	: Rated voltage			
	Charge/discharge current	: 50mA max.			
	Duration	: 500 +24/-0 hrs			
	Recovery	: 24 \pm 2hrs under the standard condition Note3			

16. High Temperatu	ure Loading					
Temperature Compensating(High Frequency type)						
	Appearance	: No abnormality				
	Capacitance change	: C‰≦10pF :±0.3pF C‰>10pF :±3%				
	Insulation resistance	:1000M Ω min				
Specified Value	High permittivity					
	Appearance	: No abnormality				
	Capacitance change	: Within ± 15%				
	Dissipation factor	: 7%max(HMK,HMJ), 5%max(QMK,QMJ, SMK,SMJ).				
	Insulation resistance	: $50M\Omega \ \mu$ F or $1000M\Omega$, whichever is smaller.				
	According to JIS 5102 clause 9.10.					
	Preconditioning	: Voltage treatment Note2 (Only High permittivity)				
Test Methods and	Temperature	: Maximum operating temperature				
Remarks	Applied voltage	: Rated voltage×2(HMK,HMJ,QVS) Rated voltage×1.5(QMK,QMJ) Rated voltage×1.2(SMK,SMJ)				
1 contained	Charge/discharge current	: 50mA max.				
	Duration	: 1000 +24/-0 hrs				
	Recovery	: 24 \pm 2hrs under the standard condition Note3				
Note1 Thermal treatm	nent : Initial value shall be measure	d after test sample is heat-treated at 150 $+$ 0 $/-$ 10 $^\circ$ C for an hour and kept at room temperature				
	for 24 ± 2 hours.					
Note2 Voltage treatme		ed after test sample is voltage-treated for an hour at both the temperature and voltage specified in				
		kept at room temperature for 24±2hours.				
Note3 Standard condi		elative humidity: 45 to 85 % RH, Air pressure: 86 to 106kPa concerning measurement results, in order to provide correlation data, the test shall be conducted				
	under the following condition					
	•	ative humidity: 60 to 70 % RH. Air pressure: 86 to 106kPa				
		all the tests are conducted under the "standard condition".				

PRECAUTIONS


1. Circuit Design	
	♦Verification of operating environment, electrical rating and performance
	1. A malfunction of equipment in fields such as medical, aerospace, nuclear control, etc. may cause serious harm to human life or have severe social ramifications.
	Therefore, any capacitors to be used in such equipment may require higher safety and reliability, and shall be clearly differentiated from them used in general purpose applications.
Precautions	♦ Operating Voltage (Verification of Rated voltage)
	1. The operating voltage for capacitors must always be their rated voltage or less.
	If an AC voltage is loaded on a DC voltage, the sum of the two peak voltages shall be the rated voltage or less.
	For a circuit where an AC or a pulse voltage may be used, the sum of their peak voltages shall also be the rated voltage or less.
	2. Even if an applied voltage is the rated voltage or less reliability of capacitors may be deteriorated in case that either a high frequency AC voltage or a pulse voltage having rapid rise time is used in a circuit.

2. PCB Design									
-	♦Pattern config	gurations (Desig	n of Land-patt	terns)					
	1. When capacitors are mounted on PCBs, the amount of solder used (size of fillet) can directly affect the capacitor performance.								
	Therefore, the following items must be carefully considered in the design of land patterns:								
	(1)Excess	sive solder applie	ed can cause	mechanical st	resses which le	ead to chip bre	aking or crack	ing. Therefore,	please consider
	appr	opriate land-patt	terns for prope	er amount of so	older.				
Precautions	(2)When r	more than one co	omponent are	jointly soldered	d onto the same	e land, each con	nponent's solde	ring point shall	be separated by
	sold	er-resist.							
	Pattern config	gurations (Capac	itor layout on	PCBs)					
	After capacito	ors are mounted	on boards, th	ey can be subj	ected to mecha	anical stresses	in subsequent ı	manufacturing p	orocesses (PCB
	cutting, board	inspection, mour	nting of additio	onal parts, asser	mbly into the ch	nassis, wave solo	dering of the bo	ards, etc.). For	this reason, land
	pattern config	urations and pos	itions of capao	citors shall be o	carefully conside	ered to minimize	e stresses.		
	Pattern config	gurations (Desig	n of Land-patt	terns)					
	The following	diagrams and tab	les show som	e examples of r	recommended la	and patterns to	prevent excess	ive solder amou	ints.
	(1)Recomme	ended land dimen	isions for typic	cal chip capacit	ors				
		r Ceramic Capac	itors : Recom	mended land di	mensions		Land pat	terns for PCBs	
	(unit: mm)							Land pattern	0.11
	Wave-so			010	0.05		Chip cap	pacitor	Solder-resist
	Туре	107	212	316	325	<u> </u>			
	Size L	1.6	2.0	3.2	3.2	c [/)
	W	0.8	1.25	1.6	2.5	(┥┝╾┺╩	่╂┅╂╾┥ ┝──′	2
	A	0.8 to 1.0	1.0 to 1.4	1.8 to 2.5	1.8 to 2.5			$\rightarrow \longleftarrow$	
	B	0.5 to 0.8	0.8 to 1.5	0.8 to 1.7	0.8 to 1.7		ВА	АВ	
	C	0.6 to 0.8	0.9 to 1.2	1.2 to 1.6	1.8 to 2.5				
							Chip ca	pacitor	
								W	
								<u></u>	
							Ĺ		
Technical	Reflow-s	oldering							
considerations	Туре	042	063	105	107	212	316	325	432
	Size L	0.4	0.6	1.0	1.6	2.0	3.2	3.2	4.5
	W	0.2	0.3	0.5	0.8	1.25	1.6	2.5	3.2
	A	0.15 to 0.25	0.20 to 0.30	0.45 to 0.55	0.8 to 1.0	0.8 to 1.2	1.8 to 2.5	1.8 to 2.5	2.5 to 3.5
	В	0.15 to 0.20	0.20 to 0.30	0.40 to 0.50	0.6 to 0.8	0.8 to 1.2	1.0 to 1.5	1.0 to 1.5	1.5 to 1.8
	С	0.15 to 0.30	0.25 to 0.40	0.45 to 0.55	0.6 to 0.8	0.9 to 1.6	1.2 to 2.0	1.8 to 3.2	2.3 to 3.5
	Note:Reco	ommended land s	size might be c	different accord	ling to the allow	ance of the size	e of the product	t.	
		Recommended la	nd dimonsions	for roflow-ook	doring		LWD	C	
	(unit: mm)				Jering				
	Туре	105	107	212)				
		0.52	0.8	1.25					
	Size W	1.0	1.6	2.0				w	
	A .	0.18 to 0.22	0.25 to 0						
	В	0.2 to 0.25	0.3 to 0.						
	C	0.9 to 1.1	1.5 to 1.				·	 	
		0.0 10 1.1	1.0 10 1.				1 -	I	



1–3. When PCB is split, the amount of mechanical stress on the capacitors can vary according to the method used. The following methods are listed in order from least stressful to most stressful: push-back, slit, V-grooving, and perforation. Thus, please consider the PCB, split methods as well as chip location.

3. Mounting	
Precautions	 Adjustment of mounting machine When capacitors are mounted on PCB, excessive impact load shall not be imposed on them. Maintenance and inspection of mounting machines shall be conducted periodically. Selection of Adhesives When chips are attached on PCBs with adhesives prior to soldering, it may cause capacitor characteristics degradation unless the following factors are appropriately checked : size of land patterns, type of adhesive, amount applied, hardening temperature and hardening period. Therefore, please contact us for further information.




	♦ Selection of Flux
	Since flux may have a significant effect on the performance of capacitors, it is necessary to verify the following conditions prior to use;
	(1) Flux used shall be less than or equal to 0.1 wt%(in Cl equivalent) of halogenated content. Flux having a strong acidity content shall not be applied.
	(2) When shall capacitors are soldered on boards, the amount of flux applied shall be controlled at the optimum level.
Precautions	(3)When water-soluble flux is used, special care shall be taken to properly clean the boards.
	◆ Soldering
	Temperature, time, amount of solder, etc. shall be set in accordance with their recommended conditions.
	Sn-Zn solder paste can adversely affect MLCC reliability.
	Please contact us prior to usage of Sn-Zn solder.
	♦ Selection of Flux
	1-1. When too much halogenated substance (Chlorine, etc.) content is used to activate flux, or highly acidic flux is used, it may lead to corrosion of terminal electrodes or degradation of insulation resistance on the surfaces of the capacitors.
Technical considerations	1-2. Flux is used to increase solderability in wave soldering. However if too much flux is applied, a large amount of flux gas may be emitted and may adversely affect the solderability. To minimize the amount of flux applied, it is recommended to use a flux-bubbling system.
	1-3. Since the residue of water-soluble flux is easily dissolved in moisture in the air, the residues on the surfaces of capacitors in high
	humidity conditions may cause a degradation of insulation resistance and reliability of the capacitors. Therefore, the cleaning
	methods and the capability of the machines used shall also be considered carefully when water-soluble flux is used.




Soldering

- · Ceramic chip capacitors are susceptible to thermal shock when exposed to rapid or concentrated heating or rapid cooling.
- Therefore, the soldering must be conducted with great care so as to prevent malfunction of the components due to excessive thermal shock.
- Preheating : Capacitors shall be preheated sufficiently, and the temperature difference between the capacitors and solder shall be within 100 to 130°C.
- · Cooling : The temperature difference between the capacitors and cleaning process shall not be greater than 100°C.



Caution

The ideal condition is to have solder mass(fillet)controlled to 1/2 to 1/3 of the thickness of a capacitor.





②Because excessive dwell times can adversely affect solderability, soldering duration shall be kept as close to recommended times as possible.

③Allowable number of reflow soldering : 2 times max.



[Recommended conditions for eutectic soldering]







Caution


OWave soldering must not be applied to capacitors designated as for reflow soldering only. OAllowable number of wave soldering : 1 times max.



[Recommended conditions for eutectic soldering] [Recommended condition for Pb-free soldering]







Caution

①Use a 50W soldering iron with a maximum tip diameter of 1.0 mm.
②The soldering iron shall not directly touch capacitors.
③Allowable number of hand soldering : 1 times max.

5. Cleaning	
Precautions	 Cleaning conditions 1. When PCBs are cleaned after capacitors mounting, please select the appropriate cleaning solution in accordance with the intended use of the cleaning. (e.g. to remove soldering flux or other materials from the production process.) 2. Cleaning condition shall be determined after it is verified by using actual cleaning machine that the cleaning process does not affect capacitor's characteristics.
Technical considerations	 The use of inappropriate cleaning solutions can cause foreign substances such as flux residue to adhere to capacitors or deteriorate their outer coating, resulting in a degradation of the capacitor's electrical properties (especially insulation resistance). Inappropriate cleaning conditions (insufficient or excessive cleaning) may adversely affect the performance of the capacitors. In the case of ultrasonic cleaning, too much power output can cause excessive vibration of PCBs which may lead to the cracking of capacitors or the soldered portion, or decrease the terminal electrodes' strength. Therefore, the following conditions shall be carefully checked; Ultrasonic output : 20 W/2 or less Ultrasonic frequency : 40 kHz or less Ultrasonic washing period : 5 min. or less

6. Resin coating a	and mold
	1. With some type of resins, decomposition gas or chemical reaction vapor may remain inside the resin during the hardening period or while left under normal storage conditions resulting in the deterioration of the capacitor's performance.
Precautions	2. When a resin's hardening temperature is higher than capacitor's operating temperature, the stresses generated by the excessive heat may lead to damage or destruction of capacitors. The use of such resins, molding materials etc. is not recommended.

7. Handling	
	 Splitting of PCB 1. When PCBs are split after components mounting, care shall be taken so as not to give any stresses of deflection or twisting to the board. 2. Board separation shall not be done manually, but by using the appropriate devices.
Precautions	 Mechanical considerations Be careful not to subject capacitors to excessive mechanical shocks. (1) If ceramic capacitors are dropped onto a floor or a hard surface, they shall not be used. (2) Please be careful that the mounted components do not come in contact with or bump against other boards or components.

	♦Storage		
	 To maintain the solderability of terminal electrodes and to keep packaging materials in good condition, care must be taken to contro temperature and humidity in the storage area. Humidity should especially be kept as low as possible. Recommended conditions 		
	Ambient temperature : Below 30°C		
D	Humidity : Below 70% RH		
Precautions	 The ambient temperature must be kept below 40°C. Even under ideal storage conditions, solderability of capacitor is deteriorated as time passes, so capacitors shall be used within 6 months from the time of delivery. Ceramic chip capacitors shall be kept where no chlorine or sulfur exists in the air. The capacitance values of high dielectric constant capacitors will gradually decrease with the passage of time, so care shall be taken to design circuits. Even if capacitance value decreases as time passes, it will get back to the initial value by a heat treatment at 150°C for 1hour. 		
Technical considerations	If capacitors are stored in a high temperature and humidity environment, it might rapidly cause poor solderability due to terminal oxidation a quality loss of taping/packaging materials. For this reason, capacitors shall be used within 6 months from the time of delivery. If exceeding t above period, please check solderability before using the capacitors.		

