











LM7321, LM7322

SNOSAW8E -MAY 2008-REVISED SEPTEMBER 2015

LM7321x Single and LM7322x Dual Rail-to-Rail Input and Output ±15-V, High-Output **Current and Unlimited Capacitive Load Operational Amplifier**


Features

- $(V_S = \pm 15, T_A = 25^{\circ}C, Typical Values Unless)$ Specified.)
- Wide Supply Voltage Range 2.5 V to 32 V
- Output Current +65 mA/-100 mA
- Gain Bandwidth Product 20 MHz
- Slew Rate 18 V/µs
- Capacitive Load Tolerance Unlimited
- Input Common-Mode Voltage 0.3-V Beyond Rails
- Input Voltage Noise 15 nV/√Hz
- Input Current Noise 1.3 pA/√Hz
- Supply Current/Channel 1.1 mA
- Distortion THD+Noise -86 dB
- Temperature Range -40°C to 125°C
- Tested at -40°C, 25°C and 125°C at 2.7 V, ±5 V, ±15 V.
- LM732xx are Automotive Grade Products that are AEC-Q100 Grade 1 Qualified.

2 Applications

- **Driving MOSFETs and Power Transistors**
- Capacitive Proximity Sensors
- **Driving Analog Optocouplers**
- High-Side Sensing
- **Below Ground Current Sensing**
- Photodiode Biasing
- **Driving Varactor Diodes in PLLs**
- Wide Voltage Range Power supplies
- Automotive
- International Power Supplies

Output Swing vs. Sourcing Current



3 Description

The LM732xx devices are rail-to-rail input and output amplifiers with wide operating voltages and highoutput currents. The LM732xx family is efficient, achieving 18-V/µs slew rate and 20-MHz unity gain bandwidth while requiring only 1 mA of supply current per op amp. The LM732xx device performance is fully specified for operation at 2.7 V, ±5 V and ±15 V.

The LM732xx devices are designed to drive unlimited capacitive loads without oscillations. All LM7321x and LM7322x parts are tested at -40°C, 125°C, and 25°C, with modern automatic test equipment. High performance from -40°C to 125°C, detailed specifications, and extensive testing makes them suitable for industrial, automotive, communications applications.

Greater than rail-to-rail input common-mode voltage range with 50 dB of common-mode rejection across this wide voltage range, allows both high-side and low-side sensing. Most device parameters are insensitive to power supply voltage, and this makes the parts easier to use where supply voltage may vary, such as automotive electrical systems and battery powered equipment. These amplifiers have true rail-to-rail output and can supply a respectable amount of current (15 mA) with minimal head-room from either rail (300 mV) at low distortion (0.05% THD+Noise).

Device Information⁽¹⁾

PART NUMBER	PACKAGE	BODY SIZE (NOM)
LM7321	SOIC (8)	4.90 mm × 3.91 mm
LM7322	SOT (5)	2.90 mm × 1.60 mm
LM7322	VSSOP (8)	3.00 mm × 3.00 mm

(1) For all available packages, see the orderable addendum at the end of the data sheet.

Large Signal Step Response






Table of Contents

1	Features 1		8.2 Functional Block Diagram	20
2	Applications 1		8.3 Feature Description	20
3	Description 1		8.4 Device Functional Modes	23
4	Revision History2	9	Application and Implementation	25
5	Description continued		9.1 Application Information	25
6	Pin Configuration and Functions		9.2 Typical Application	25
7	Specifications4	10	Power Supply Recommendations	<mark>27</mark>
′	7.1 Absolute Maximum Ratings	11	Layout	<mark>27</mark>
	7.1 Absolute Maximum Ratings		11.1 Layout Guidelines	27
	7.3 Recommended Operating Conditions		11.2 Layout Example	27
	7.4 Thermal Information	12	Device and Documentation Support	28
	7.5 2.7-V Electrical Characteristics		12.1 Related Links	28
	7.6 ±5-V Electrical Characteristics		12.2 Community Resources	28
	7.7 ±15-V Electrical Characteristics		12.3 Trademarks	28
	7.8 Typical Characteristics		12.4 Electrostatic Discharge Caution	28
8	Detailed Description		12.5 Glossary	28
•	8.1 Overview	13	Mechanical, Packaging, and Orderable Information	28

4 Revision History

NOTE: Page numbers for previous revisions may differ from page numbers in the current version.

Changes from Revision D (March 2013) to Revision E

Page

Changes from Revision C (May 2008) to Revision D


Page




5 Description continued


There are several package options for each part. Standard SOIC versions of both parts make upgrading existing designs easy. LM7322x are offered in a space-saving 8-Pin VSSOP package. The LM7321x are offered in small SOT-23 package, which makes it easy to place this part close to sensors for better circuit performance.

Pin Configuration and Functions









Pin Functions

		PIN				
NAME	SOT-23 NO.	SOIC NO.	VSSOP, SOIC NO.	I/O	DESCRIPTION	
OUT	1	6	_	0	Output	
OUT A	_	_	1	0	Output for Amplifier A	
OUT B	_	_	7	0	Output for Amplifier B	
V+	5	7	7	Р	Positive Supply	
V-	2	4	4	Р	Negative Supply	
+IN	3	3	_	I	Noninverting Input	
-IN	4	2	_	I	Inverting Input	
+IN A	_	_	3	I	Noninverting Input for Amplifier A	
-IN A	_	_	2	I	Inverting Input for Amplifier A	
+IN B	_	_	5	I	Noninverting Input for Amplifier B	
–IN B	_	_	6	I	Inverting Input for Amplifier B	
N/C	_	1, 5, 8	_	_	No connection	

Copyright © 2008-2015, Texas Instruments Incorporated Submit Documentation Feedback



7 Specifications

7.1 Absolute Maximum Ratings

over operating free-air temperature range (unless otherwise noted)⁽¹⁾⁽²⁾

		MIN	MAX	UNIT
V _{IN} Differential			±10	V
Output Short Cir	rcuit Current	See	e ⁽³⁾	
Supply Voltage	$(V_S = V^+ - V^-)$		35	V
Voltage at Input	/Output pins	V ⁺ + 0.8	V ⁻ - 0.8	V
Junction Tempe	rature ⁽⁴⁾		150	°C
Soldering	Infrared or Convection (20 sec.)		235	°C
Information:	Wave Soldering (10 sec.)		260	°C
Storage Temperature		-65	150	°C

- (1) Stresses beyond those listed under Absolute Maximum Ratings may cause permanent damage to the device. These are stress ratings only, which do not imply functional operation of the device at these or any other conditions beyond those indicated under Recommended Operating Conditions. Exposure to absolute-maximum-rated conditions for extended periods may affect device reliability.
- (2) If Military/Aerospace specified devices are required, please contact the Texas Instruments Sales Office/Distributors for availability and specifications.
- (3) Applies to both single-supply and split-supply operation. Continuous short circuit operation at elevated ambient temperature can result in exceeding the maximum allowed junction temperature of 150°C. Short circuit test is a momentary test. Output short circuit duration is infinite for V_S ≤ 6V at room temperature and below. For V_S > 6V, allowable short circuit duration is 1.5 ms.
- (4) The maximum power dissipation is a function of $T_{J(MAX)}$, $\vec{R}_{\theta JA}$. The maximum allowable power dissipation at any ambient temperature is $P_D = (T_{J(MAX)}) T_A / R_{\theta JA}$. All numbers apply for packages soldered directly onto a PCB.

7.2 ESD Ratings

			VALUE	UNIT
		Human body model (HBM), per ANSI/ESDA/JEDEC JS-001 (2)	±2000	
V _(ESD)	Electrostatic discharge (1)	Charged-device model (CDM), per JEDEC specification JESD22-C101 ⁽³⁾	±1000	V
		Machine Model	200	

- (1) Human Body Model, applicable std. MIL-STD-883, Method 3015.7. Machine Model, applicable std. JESD22-A115-A (ESD MM std. of JEDEC)Field-Induced Charge-Device Model, applicable std. JESD22-C101-C (ESD FICDM std. of JEDEC).
- (2) JEDEC document JEP155 states that 500-V HBM allows safe manufacturing with a standard ESD control process.
- (3) JEDEC document JEP157 states that 250-V CDM allows safe manufacturing with a standard ESD control process.

7.3 Recommended Operating Conditions

	MIN	MAX	UNIT
Supply Voltage $(V_S = V^+ - V^-)$	2.5	32	V
Temperature Range ⁽¹⁾	-40	125	°C

⁽¹⁾ The maximum power dissipation is a function of $T_{J(MAX)}$, $R_{\theta JA}$. The maximum allowable power dissipation at any ambient temperature is $P_D = (T_{J(MAX)}) - T_A / R_{\theta JA}$. All numbers apply for packages soldered directly onto a PCB.

7.4 Thermal Information

			LM7321		
	THERMAL METRIC ⁽¹⁾	D (SOIC)	DBV (SOT)	DGK (VSSOP)	UNIT
		8 PINS	5 PINS	8 PINS	
$R_{\theta JA}^{(2)}$	Junction-to-ambient thermal resistance	165	325	235	°C/W

- For more information about traditional and new thermal metrics, see the Semiconductor and IC Package Thermal Metrics application report. SPRA953
- (2) The maximum power dissipation is a function of $T_{J(MAX)}$, $R_{\theta JA}$. The maximum allowable power dissipation at any ambient temperature is $P_D = (T_{J(MAX)}) T_A / R_{\theta JA}$. All numbers apply for packages soldered directly onto a PCB.

Submit Documentation Feedback

Copyright © 2008–2015, Texas Instruments Incorporated



7.5 2.7-V Electrical Characteristics

Unless otherwise specified, all limits ensured for T_A = 25°C, V^+ = 2.7 V, V^- = 0 V, V_{CM} = 0.5 V, V_{OUT} = 1.35 V, and R_L > 1 M Ω to 1.35 V.⁽¹⁾

	PARAMETER	TEST COND	ITION	MIN ⁽²⁾	TYP ⁽³⁾	MAX ⁽²⁾	UNIT	
	logert Offerst Vallage	V 05V == 1V 03V		- 5	±0.7	+5	\ /	
Vos	Input Offset Voltage	$V_{CM} = 0.5 \text{ V}$ and $V_{CM} = 2.2 \text{ V}$	$T_A = -40^{\circ}\text{C to } +125^{\circ}\text{C}$	-6		+6	mV	
TC V _{OS}	Input Offset Voltage Temperature Drift	$V_{CM} = 0.5 \text{ V} \text{ and } V_{CM} = 2.2 \text{ V}^{(4)}$	9)		±2		μV/C	
		$V_{CM} = 0.5 V^{(5)}$		-2	-1.2			
	Input Bias Current	VCM = 0.3 V	$T_A = -40^{\circ}\text{C to } +125^{\circ}\text{C}$	-2.5			μA	
I _B		V _{CM} = 2.2 V ⁽⁵⁾			0.45	1	μΛ	
		V _{CM} = 2.2 V · /	$T_A = -40^{\circ}\text{C to } +125^{\circ}\text{C}$			1.5		
	Input Offeet Current	\/ - 0 5 \/ and \/ - 2 2 \/			20	200	nA	
I _{OS}	Input Offset Current	$V_{CM} = 0.5 \text{ V} \text{ and } V_{CM} = 2.2 \text{ V}$	$T_A = -40^{\circ}\text{C to } +125^{\circ}\text{C}$			300	IIA	
		0 V ≤ V _{CM} ≤ 1 V		70	100			
CMRR	Common-Mode	O A Z ACW Z I A	$T_A = -40^{\circ}\text{C to } +125^{\circ}\text{C}$	60			٩D	
	Rejection Ratio	0.1/2.1/ / 2.7.1/		55	70		dB	
		$0 \text{ V} \leq \text{V}_{\text{CM}} \leq 2.7 \text{ V}$	$T_A = -40^{\circ}\text{C to } +125^{\circ}\text{C}$	50				
PSRR	Power Supply Rejection	271/21/2201/		78	104	dB	٩D	
FORK	Ratio	2.7 V ≤ V _S ≤ 30 V	$T_A = -40^{\circ}\text{C to } +125^{\circ}\text{C}$	74				
	Common-Mode Voltage Range (Min)	CMDD . TO AD			-0.3	-0.1	V	
CM//D		CMRR > 50 dB	$T_A = -40^{\circ}\text{C to } +125^{\circ}\text{C}$			0		
CMVR	Common-Mode Voltage Range (Max)	CMRR > 50 dB		2.8	3			
			$T_A = -40^{\circ}\text{C to } +125^{\circ}\text{C}$	2.7				
	•	$0.5 \text{ V} \le \text{V}_{\text{O}} \le 2.2 \text{ V}$		65	72			
^	On an I am Maltana Cain	$R_L = 10 \text{ k}\Omega \text{ to } 1.35 \text{ V}$	$T_A = -40^{\circ}\text{C to } +125^{\circ}\text{C}$	62			٩D	
A _{VOL}	Open-Loop Voltage Gain	$0.5 \text{ V} \le \text{V}_{\text{O}} \le 2.2 \text{ V}$		59	66		dB	
		$R_L = 2 k\Omega$ to 1.35V	$T_A = -40^{\circ}\text{C to } +125^{\circ}\text{C}$	55				
		$R_L = 10 \text{ k}\Omega \text{ to } 1.35 \text{ V}$			50	150		
	Output Voltage Swing	$V_{ID} = 100 \text{ mV}$	$T_A = -40^{\circ}\text{C to } +125^{\circ}\text{C}$			160		
	High	$R_L = 2 k\Omega$ to 1.35 V			100	250		
		$V_{ID} = 100 \text{ mV}$	$T_A = -40^{\circ}\text{C to } +125^{\circ}\text{C}$			280	mV from	
V _{OUT}		$R_L = 10 \text{ k}\Omega \text{ to } 1.35 \text{ V}$			20	120	either rail	
	Output Voltage Swing	$V_{ID} = -100 \text{ mV}$	$T_A = -40^{\circ}\text{C to } +125^{\circ}\text{C}$			150	†	
	Low	$R_L = 2 \text{ k}\Omega \text{ to } 1.35 \text{ V}$			40	120		
		V _{ID} = −100 mV	$T_A = -40^{\circ}\text{C to } +125^{\circ}\text{C}$			150	1	
		Sourcing		30	48			
		$V_{ID} = 200 \text{ mV}, V_{OUT} = 0 \text{ V}^{(6)}$	$T_A = -40^{\circ}\text{C to } +125^{\circ}\text{C}$	20			mA	
I _{OUT}	Output Current	Sinking		40	65			
			$V_{ID} = -200 \text{ mV}, V_{OUT} = 2.7$ $V^{(6)}$	$T_A = -40^{\circ}\text{C to } +125^{\circ}\text{C}$	30			

⁽¹⁾ Electrical Table values apply only for factory testing conditions at the temperature indicated. Factory testing conditions result in very limited self-heating of the device such that T_J = T_A. No ensured specification of parametric performance is indicated in the electrical tables under conditions of internal self-heating where T_J > T_A.

Copyright © 2008–2015, Texas Instruments Incorporated

⁽²⁾ All limits are ensured by testing or statistical analysis.

⁽³⁾ Typical values represent the most likely parametric norm as determined at the time of characterization. Actual typical values may vary over time and will also depend on the application and configuration. The typical values are not tested and are not ensured on shipped production material.

⁽⁴⁾ Offset voltage temperature drift determined by dividing the change in V_{OS} at temperature extremes into the total temperature change.

⁵⁾ Positive current corresponds to current flowing into the device.

⁽⁶⁾ Applies to both single-supply and split-supply operation. Continuous short circuit operation at elevated ambient temperature can result in exceeding the maximum allowed junction temperature of 150°C. Short circuit test is a momentary test. Output short circuit duration is infinite for V_S ≤ 6 V at room temperature and below. For V_S > 6 V, allowable short circuit duration is 1.5 ms.



2.7-V Electrical Characteristics (continued)

Unless otherwise specified, all limits ensured for T_A = 25°C, V^+ = 2.7 V, V^- = 0 V, V_{CM} = 0.5 V, V_{OUT} = 1.35 V, and R_L > 1 M Ω to 1.35 V.⁽¹⁾

	PARAMETER	TEST COND	ITION	MIN ⁽²⁾	TYP ⁽³⁾	MAX ⁽²⁾	UNIT
		LM7224			0.95	1.3	
	Committee Committee	LM7321	$T_A = -40^{\circ}\text{C to } +125^{\circ}\text{C}$			1.9	A
IS	Supply Current	LM7222			2	2.5	mA
		LM7322	$T_A = -40^{\circ}\text{C to } +125^{\circ}\text{C}$			3.8	
SR	Slew Rate ⁽⁷⁾	$A_V = +1, V_I = 2-V \text{ Step}$			8.5		V/µs
f _u	Unity Gain Frequency	$R_L = 2 k\Omega$, $C_L = 20 pF$			7.5		MHz
GBW	Gain Bandwidth	f = 50 kHz			16		MHz
e _n	Input Referred Voltage Noise Density	f = 2 kHz			11.9		nV/√ H
i _n	Input Referred Current Noise Density	f = 2 kHz			0.5		pA/√ H
THD+N	Total Harmonic Distortion + Noise	$V^{+} = 1.9 \text{ V}, V^{-} = -0.8 \text{ V}$ $f = 1 \text{ kHz}, R_{L} = 100 \text{ k}\Omega, A_{V} = +$ $V_{OUT} = 210 \text{ mV}_{PP}$	2		- 77		dB
CT Rej.	Crosstalk Rejection	$f = 100 \text{ kHz}$, Driver $R_L = 10 \text{ k}\Omega$			60		dB

⁽⁷⁾ Slew rate is the slower of the rising and falling slew rates. Connected as a Voltage Follower.



7.6 ±5-V Electrical Characteristics

Unless otherwise specified, all limited ensured for $T_A = 25^{\circ}C$, $V^+ = 5$ V, $V^- = -5$ V, $V_{CM} = 0$ V, $V_{OUT} = 0$ V, and $R_L > 1$ M Ω to 0 V. $^{(1)}$

	PARAMETER	TES	TCONDITION	MIN ⁽²⁾	TYP ⁽³⁾	MAX ⁽²⁾	UNIT
1/	Input Offact Voltage	$V_{CM} = -4.5 \text{ V}$ and $V_{CM} =$		-5	±0.7	+5	mV
Vos	Input Offset Voltage	4.5 V	$T_A = -40^{\circ}\text{C to } +125^{\circ}\text{C}$	-6		+6	IIIV
TC V _{OS}	Input Offset Voltage Temperature Drift	$V_{CM} = -4.5 \text{ V} \text{ and } V_{CM} = 4.$	5 V ⁽⁴⁾		±2		μV/°C
		$V_{CM} = -4.5 V^{(5)}$		-2.0	-1.2		
	Innut Piga Current		$T_A = -40^{\circ}C \text{ to } +125^{\circ}C$	-2.5			
IB	Input Bias Current	$V_{CM} = 4.5 V^{(5)}$			0.45	1	μA
			$T_A = -40^{\circ}C \text{ to } +125^{\circ}C$			1.5	
	Innut Offact Current	$V_{CM} = -4.5 \text{ V}$ and $V_{CM} =$			20	200	~ Λ
los	Input Offset Current	4.5 V	$T_A = -40^{\circ}\text{C to } +125^{\circ}\text{C}$			300	nA
		5.V.s.V 2.V.		80	100		
OMPR	Common Mode	$-5 \text{ V} \leq \text{V}_{\text{CM}} \leq 3 \text{ V}$	$T_A = -40$ °C to +125°C	70			.ID
CMRR	Rejection Ratio	577.77		65	80		dB
		-5 V ≤ V _{CM} ≤ 5 V	$T_A = -40^{\circ}\text{C to } +125^{\circ}\text{C}$	62			
	Power Supply Rejection Ratio	$2.7 \text{ V} \le \text{V}_{\text{S}} \le 30 \text{ V},$		78	104		dB
PSRR			$T_A = -40^{\circ}\text{C to } +125^{\circ}\text{C}$	74			
	Common-Mode Voltage Range (Min)	CMRR > 50 dB			-5.3	-5.1	V
			$T_A = -40^{\circ}\text{C to } +125^{\circ}\text{C}$			-5	
CMVR	Common-Mode Voltage Range (Max)	CMRR > 50 dB		5.1	5.3		
			$T_A = -40^{\circ}\text{C to } +125^{\circ}\text{C}$	5			
	!	$-4 \text{ V} \leq \text{V}_{\text{O}} \leq 4 \text{ V}$ $R_{\text{L}} = 10 \text{ k}\Omega \text{ to } 0 \text{ V}$		74	80		dB
	Open-Loop Voltage		$T_A = -40^{\circ}\text{C to } +125^{\circ}\text{C}$	70			
A_{VOL}	Gain	-4 V ≤ V _O ≤ 4 V		68	74		
		$R_L = 2 k\Omega \text{ to } 0 \text{ V}$	$T_A = -40^{\circ}\text{C to } +125^{\circ}\text{C}$	65			
		$R_L = 10 \text{ k}\Omega \text{ to } 0 \text{ V}$	7		100	250	
	Output Voltage Swing	$V_{ID} = 100 \text{ mV}$	$T_A = -40^{\circ}\text{C to } +125^{\circ}\text{C}$			280	
	High	$R_L = 2 k\Omega$ to 0 V	A		160	350	
		$V_{ID} = 100 \text{ mV}$	$T_A = -40^{\circ}\text{C} \text{ to } +125^{\circ}\text{C}$			450	mV from
V_{OUT}		$R_L = 10 \text{ k}\Omega \text{ to } 0 \text{ V}$	^		35	200	either
	Output Voltage Swing	$V_{ID} = -100 \text{ mV}$	$T_A = -40^{\circ}\text{C to } +125^{\circ}\text{C}$			250	rail
	Low	$R_L = 2 k\Omega$ to 0 V			80	200	
		$V_{ID} = -100 \text{ mV}$	$T_A = -40^{\circ}\text{C to } +125^{\circ}\text{C}$			250	
	<u> </u>	Sourcing	,	35	70		
	Output Current	V _{ID} = 200 mV, V _{OUT} = -5 V ⁽⁶⁾	$T_A = -40^{\circ}\text{C to } +125^{\circ}\text{C}$	20			-
I _{OUT}	Output Current	tput Current Sinking		50	85		mA
		V _{ID} = -200 mV, V _{OUT} = 5 V ⁽⁶⁾	$T_A = -40^{\circ}\text{C to } +125^{\circ}\text{C}$	30			

⁽¹⁾ Electrical Table values apply only for factory testing conditions at the temperature indicated. Factory testing conditions result in very limited self-heating of the device such that T_J = T_A. No ensured specification of parametric performance is indicated in the electrical tables under conditions of internal self-heating where T_J > T_A.

Submit Documentation Feedback

⁽²⁾ All limits are ensured by testing or statistical analysis.

⁽³⁾ Typical values represent the most likely parametric norm as determined at the time of characterization. Actual typical values may vary over time and will also depend on the application and configuration. The typical values are not tested and are not ensured on shipped production material.

⁽⁴⁾ Offset voltage temperature drift determined by dividing the change in V_{OS} at temperature extremes into the total temperature change.

⁵⁾ Positive current corresponds to current flowing into the device.

⁽⁶⁾ Applies to both single-supply and split-supply operation. Continuous short circuit operation at elevated ambient temperature can result in exceeding the maximum allowed junction temperature of 150°C. Short circuit test is a momentary test. Output short circuit duration is infinite for V_S ≤ 6 V at room temperature and below. For V_S > 6 V, allowable short circuit duration is 1.5 ms.



±5-V Electrical Characteristics (continued)

Unless otherwise specified, all limited ensured for $T_A = 25^{\circ}C$, $V^+ = 5$ V, $V^- = -5$ V, $V_{CM} = 0$ V, $V_{OUT} = 0$ V, and $R_L > 1$ M Ω to 0 V. $^{(1)}$

	PARAMETER	Ti	EST CONDITION		MIN ⁽²⁾	TYP ⁽³⁾	MAX ⁽²⁾	UNIT
						1.0	1.3	
	Disply Courses	V 45V	LM7321	$T_A = -40^{\circ}\text{C to} +125^{\circ}\text{C}$			2	
I _S	Supply Current	$V_{CM} = -4.5 \text{ V}$				2.3	2.8	mA
			LM7322	$T_A = -40^{\circ}C$ to +125°C			3.8	
SR	Slew Rate ⁽⁷⁾	$A_V = +1, V_I = 8-V \text{ Step}$				12.3		V/µs
f _u	Unity Gain Frequency	$R_L = 2 k\Omega$, $C_L = 20 pF$				9		MHz
GBW	Gain Bandwidth	f = 50 kHz				16		MHz
e _n	Input Referred Voltage Noise Density	f = 2 kHz				14.3		nV/√H
i _n	Input Referred Current Noise Density	f = 2 kHz				1.35		pA/√ H
THD+N	Total Harmonic Distortion + Noise	$f = 1 \text{ kHz}, R_L = 100 \text{ k}\Omega, A_L = 100 \text{ k}\Omega$	A _V = +2			-79		dB
CT Rej.	Crosstalk Rejection	f = 100 kHz, Driver R _L =	10 kΩ	·		60		dB

⁽⁷⁾ Slew rate is the slower of the rising and falling slew rates. Connected as a Voltage Follower.

7.7 ±15-V Electrical Characteristics

Unless otherwise specified, all limited ensured for $T_A = 25^{\circ}C$, $V^+ = 15$ V, $V^- = -15$ V, $V_{CM} = 0$ V, $V_{OUT} = 0$ V, and $R_L > 1$ M Ω to 15 V. $^{(1)}$

	PARAMETER	TE	EST CONDITION	MIN ⁽²⁾	TYP ⁽³⁾	MAX ⁽²⁾	UNIT
V	Input Offset Voltage	V _{CM} = −14.5 V and		-6	±0.7	+6	mV
Vos	input Onset voltage	$V_{CM} = 14.5 \text{ V}$	-40°C to +125°C	-8		+8	IIIV
TC V _{OS}	Input Offset Voltage Temperature Drift	$V_{CM} = -14.5 \text{ V} \text{ and } V_{CM}$	= 14.5 V ⁽⁴⁾		±2		μV/°C
		V 445 V(5)		-2	-1.1		
	$V_{CM} = -14.5 V^{(5)}$	-40°C to +125°C	-2.5				
I _B	Input Bias Current	$V_{CM} = 14.5 V^{(5)}$			0.45	1	μΑ
		V _{CM} = 14.5 V ^(c)	-40°C to +125°C			1.5	
	land Offert Comment	V _{CM} = −14.5 V and			30	300	^
los	Input Offset Current	V _{CM} = 14.5 V	-40°C to +125°C			500	nA
		15 \/ < \/ < 10 \/		80	100		
CMRR	Common-Mode Rejection	-15 V ≤ V _{CM} ≤ 12 V	-40°C to +125°C	75			dB
CIVIKK	Ratio	45 \\ < \\ < 45 \\		72	80		uБ
		-15 V ≤ V _{CM} ≤ 15 V	-40°C to +125°C	70			
DCDD	SRR Power Supply Rejection $2.7 \text{ V} \le \text{V}_{\text{S}} \le 30 \text{ V} = -14.5 \text{ V}$	$2.7 \text{ V} \le \text{V}_{\text{S}} \le 30 \text{ V}, \text{V}_{\text{CM}}$		78	100		٩D
PORK			-40°C to +125°C	74			dB

Submit Documentation Feedback

⁽¹⁾ Electrical Table values apply only for factory testing conditions at the temperature indicated. Factory testing conditions result in very limited self-heating of the device such that T_J = T_A. No ensured specification of parametric performance is indicated in the electrical tables under conditions of internal self-heating where T_J > T_A.

⁽²⁾ All limits are ensured by testing or statistical analysis.

⁽³⁾ Typical values represent the most likely parametric norm as determined at the time of characterization. Actual typical values may vary over time and will also depend on the application and configuration. The typical values are not tested and are not ensured on shipped production material.

⁽⁴⁾ Offset voltage temperature drift determined by dividing the change in VOS at temperature extremes into the total temperature change.

⁽⁵⁾ Positive current corresponds to current flowing into the device.



±15-V Electrical Characteristics (continued)


Unless otherwise specified, all limited ensured for $T_A = 25^{\circ}C$, $V^+ = 15$ V, $V^- = -15$ V, $V_{CM} = 0$ V, $V_{OUT} = 0$ V, and $R_L > 1$ M Ω to 15 V.⁽¹⁾

	PARAMETER	T	EST COND	ITION	MIN ⁽²⁾	TYP ⁽³⁾	MAX ⁽²⁾	UNIT	
	Common-Mode Voltage	CMDD - 50 dD				-15.3	-15.1		
CM//D	Range (Min)	CMRR > 50 dB	-40°C to	+125°C			-15		
CMVR	Common-Mode Voltage	CMDD . TO 4D			15.1	15.3		V	
	Range (Max)	CMRR > 50 dB	–40°C to	+125°C	15				
		-13 V ≤ V _O ≤ 13 V			75	85			
_	Onen Leen Voltage Coin	$R_L = 10 \text{ k}\Omega \text{ to } 0 \text{ V}$	–40°C to	+125°C	70			dB	
A _{VOL}	Open-Loop Voltage Gain	-13 V ≤ V _O ≤ 13 V			70	78		uБ	
		$R_L = 2 k\Omega$ to 0 V	–40°C to	+125°C	65				
		$R_1 = 10 \text{ k}\Omega \text{ to } 0 \text{ V}$				150	300		
	Output Voltage Swing	$V_{ID} = 100 \text{ mV}$	-40°C to	+125°C			350		
	High	$R_L = 2 k\Omega \text{ to } 0 \text{ V}$				250 550			
\/		$V_{ID} = 100 \text{ mV}$	–40°C to	+125°C			650	mV from	
V _{OUT}	Output Voltage Swing Low		$R_L = 10 \text{ k}\Omega \text{ to } 0 \text{ V}$				60	200	either
		V _{ID} = −100 mV	–40°C to	+125°C			250	rail	
		$R_L = 2 k\Omega$ to 0 V				130	300		
		V _{ID} = −100 mV	–40°C to	+125°C			400		
	Outrast Comment	Sourcing V _{ID} = 200 mV, V _{OUT} = -	-15 V ⁽⁶⁾		40	65		A	
I _{OUT}	Output Current	Sinking V _{ID} = −200 mV, V _{OUT} =	15 V ⁽⁶⁾		60	100		mA	
			1.1.47004			1.1	1.7		
	0	\\\\\\\\\\\\\\\\\\\\\\\\\\\\\\\\\\\\\\	LM7321	-40°C to +125°C			2.4	mA	
I _S	Supply Current	$V_{CM} = -14.5 \text{ V}$	1.1.47000			2.5	4		
			LM7322	-40°C to +125°C			5.6		
SR	Slew Rate ⁽⁷⁾	A _V = +1, V _I = 20-V Step)			18		V/µs	
f _u	Unity Gain Frequency	$R_L = 2 k\Omega$, $C_L = 20 pF$				11.3		MHz	
GBW	Gain Bandwidth	f = 50 kHz		20		MHz			
e _n	Input Referred Voltage Noise Density	f = 2 kHz				15		nV/√H	
i _n	Input Referred Current Noise Density	f = 2 kHz		1.3		pA/√ H			
THD+N	Total Harmonic Distortion +Noise	$f = 1 \text{ kHz}, R_L 100 \text{ k}Ω,$ $A_V = +2, V_{OUT} = 23 V_{PP}$		-86		dB			
CT Rej.	Crosstalk Rejection	f = 100 kHz, Driver R _L =	= 10 kΩ			60		dB	


Applies to both single-supply and split-supply operation. Continuous short circuit operation at elevated ambient temperature can result in exceeding the maximum allowed junction temperature of 150°C. Short circuit test is a momentary test. Output short circuit duration is infinite for $V_S \le 6$ V at room temperature and below. For $V_S > 6$ V, allowable short circuit duration is 1.5 ms. (7) Slew rate is the slower of the rising and falling slew rates. Connected as a Voltage Follower.



7.8 Typical Characteristics









TEXAS INSTRUMENTS

Typical Characteristics (continued)









TEXAS INSTRUMENTS

Typical Characteristics (continued)








TEXAS INSTRUMENTS

Typical Characteristics (continued)

Unless otherwise specified: $T_A = 25$ °C.






Figure 38. Positive Output Swing vs. Supply Voltage




Figure 39. Positive Output Swing vs. Supply Voltage




Figure 40. Negative Output Swing vs. Supply Voltage




Figure 41. Negative Output Swing vs. Supply Voltage




Figure 42. Open-Loop Frequency Response with Various Capacitive Load

Submit Documentation Feedback



Unless otherwise specified: $T_A = 25$ °C.






Figure 48. -PSRR vs. Frequency

Figure 47. +PSRR vs. Frequency












Figure 56. THD+N vs. Output Amplitude




Figure 57. THD+N vs. Output Amplitude



8 Detailed Description


8.1 Overview

The LM732xx devices are rail-to-rail input and output amplifiers with wide operating voltages and high-output currents. The LM732xx family is efficient, achieving 18-V/µs slew rate and 20-MHz unity gain bandwidth while requiring only 1 mA of supply current per op amp. The LM732xx device performance is fully specified for operation at 2.7 V, ±5 V and ±15 V.

The LM732xx devices are designed to drive unlimited capacitive loads without oscillations. All LM7321x and LM7322x parts are tested at -40°C, 125°C, and 25°C, with modern automatic test equipment. High performance from -40°C to 125°C, detailed specifications, and extensive testing makes them suitable for industrial, automotive, and communications applications.

Greater than rail-to-rail input common-mode voltage range with 50 dB of common-mode rejection across this wide voltage range, allows both high-side and low-side sensing. Most device parameters are insensitive to power supply voltage, and this makes the parts easier to use where supply voltage may vary, such as automotive electrical systems and battery-powered equipment. These amplifiers have true rail-to-rail output and can supply a respectable amount of current (15 mA) with minimal head room from either rail (300 mV) at low distortion (0.05% THD+Noise).

8.2 Functional Block Diagram



8.3 Feature Description

8.3.1 Output Short Circuit Current and Dissipation Issues

The LM732xx output stage is designed for maximum output current capability. Even though momentary output shorts to ground and either supply can be tolerated at all operating voltages, longer lasting short conditions can cause the junction temperature to rise beyond the absolute maximum rating of the device, especially at higher supply voltage conditions. Below supply voltage of 6 V, the output short circuit condition can be tolerated indefinitely.

With the op amp tied to a load, the device power dissipation consists of the quiescent power due to the supply current flow into the device, in addition to power dissipation due to the load current. The load portion of the power itself could include an average value (due to a DC load current) and an AC component. DC load current would flow if there is an output voltage offset, or the output AC average current is non-zero, or if the op amp operates in a single supply application where the output is maintained somewhere in the range of linear operation.

Therefore,

$$P_{TOTAL} = P_O + P_{DC} + P_{AC} \tag{1}$$



Feature Description (continued)

The Op Amp Quiescent Power Dissipation is calculated as:

$$P_Q = I_S \times V_S$$

where

I_S: Supply Current

•
$$V_S$$
: Total Supply Voltage $(V^+ - V^-)$ (2)

The DC Load Power is calculated as:

$$P_{DC} = I_O \times (V_r - V_o)$$

where

• V_O: Average Output Voltage

The AC Load Power is calculated as P_{AC} = See Table 1.

Table 1 shows the maximum AC component of the load power dissipated by the op amp for standard Sinusoidal, Triangular, and Square Waveforms:

Table 1. Normalized AC Power Dissipated in the Output Stage for Standard Waveforms

	P_{AC} (W. Ω /V ²)	
Sinusoidal	Triangular	Square
50.7×10^{-3}	46.9 × 10 ⁻³	62.5 × 10 ⁻³

The table entries are normalized to V_S^2/R_L . To figure out the AC load current component of power dissipation, simply multiply the table entry corresponding to the output waveform by the factor V_S^2/R_L . For example, with ± 12 -V supplies, a 600- Ω load, and triangular waveform power dissipation in the output stage is calculated as:

$$P_{AC} = (46.9 \times 10^{-3}) \times (242/600) = 45.0 \text{ mW}$$
 (4)

The maximum power dissipation allowed at a certain temperature is a function of maximum die junction temperature ($T_{J(MAX)}$) allowed, ambient temperature T_A , and package thermal resistance from junction to ambient, θ_{JA} .

$$P_{D(MAX)} = \frac{T_{J(MAX)} - T_A}{\theta_{JA}}$$
 (5)

For the LM732xx, the maximum junction temperature allowed is 150°C at which no power dissipation is allowed. The power capability at 25°C is given by the following calculations:

For VSSOP package:

$$P_{D(MAX)} = \frac{150 \text{°C} - 25 \text{°C}}{235 \text{°C/W}} = 0.53 \text{ W}$$
 (6)

For SOIC package:

$$P_{D(MAX)} = \frac{150^{\circ} C - 25^{\circ} C}{165^{\circ} C/W} = 0.76 \text{ W}$$
 (7)

Similarly, the power capability at 125°C is given by:

For VSSOP package:

$$P_{D(MAX)} = \frac{150 \,\text{°C} - 125 \,\text{°C}}{235 \,\text{°C/W}} = 0.11 \,\text{W}$$
(8)

For SOIC package:

$$P_{D(MAX)} = \frac{150^{\circ}C - 125^{\circ}C}{165^{\circ}C/W} = 0.15 \text{ W}$$
 (9)

Figure 58 shows the power capability vs. temperature for VSSOP and SOIC packages. The area under the maximum thermal capability line is the operating area for the device. When the device works in the operating area where P_{TOTAL} is less than $P_{D(MAX)}$, the device junction temperature will remain below 150°C. If the intersection of ambient temperature and package power is above the maximum thermal capability line, the junction temperature will exceed 150°C and this should be strictly prohibited.






Figure 58. Power Capability vs. Temperature

When high power is required and ambient temperature can't be reduced, providing air flow is an effective approach to reduce thermal resistance therefore to improve power capability.

8.3.2 Estimating the Output Voltage Swing

It is important to keep in mind that the steady-state output current will be less than the current available when there is an input overdrive present. For steady-state conditions, the Output Voltage vs. Output Current plot (*Typical Characteristics* section) can be used to predict the output swing. Figure 59 and Figure 60 show this performance along with several load lines corresponding to loads tied between the output and ground. In each cases, the intersection of the device plot at the appropriate temperature with the load line would be the typical output swing possible for that load. For example, a 1-k Ω load can accommodate an output swing to within 250 mV of V⁻ and to 330 mV of V⁺ (V_S = ±15 V) corresponding to a typical 29.3 V_{PP} unclipped swing.





Submit Documentation Feedback

Copyright © 2008–2015, Texas Instruments Incorporated



8.4 Device Functional Modes

8.4.1 Driving Capacitive Loads

The LM732xx are specifically designed to drive unlimited capacitive loads without oscillations as shown in Figure 61.





Figure 61. ±5% Settling Time vs. Capacitive Load

In addition, the output current handling capability of the device allows for good slewing characteristics even with large capacitive loads as shown in Figure 62 and Figure 63.



The combination of these features is ideal for applications such as TFT flat panel buffers, A/D converter input amplifiers, and so forth.

However, as in most op amps, addition of a series isolation resistor between the op amp and the capacitive load improves the settling and overshoot performance.

Output current drive is an important parameter when driving capacitive loads. This parameter will determine how fast the output voltage can change. Referring to the Slew Rate vs. Capacitive Load Plots (*Typical Characteristics* section), two distinct regions can be identified. Below about 10,000 pF, the output Slew Rate is solely determined by the compensation capacitor value of the op amp and available current into that capacitor. Beyond 10 nF, the Slew Rate is determined by the available output current of the op amp.

Copyright © 2008–2015, Texas Instruments Incorporated

Submit Documentation Feedback



Device Functional Modes (continued)

NOTE

Because of the lower output sourcing current compared to the sinking one, the Slew Rate limit under heavy capacitive loading is determined by the positive transitions.

An estimate of positive and negative slew rates for loads larger than 100 nF can be made by dividing the short circuit current value by the capacitor.

For the LM732xx, the available output current increases with the input overdrive. Referring to Figure 64 and Figure 65, it can be seen that both sourcing and sinking short circuit current increase as input overdrive increases. In a closed-loop amplifier configuration, during transient conditions while the fed back output has not quite caught up with the input, there will be an overdrive imposed on the input allowing more output current than would normally be available under steady-state condition. Because of this feature, the output stage quiescent current of the op amp can be kept to a minimum, thereby reducing power consumption, while enabling the device to deliver large output current when the need arises (such as during transients).




Figure 66 shows the output voltage, output current, and the resulting input overdrive with the device set for $A_V = +1$ and the input tied to a 1- V_{PP} step function driving a 47-nF capacitor. As can be seen, during the output transition, the input overdrive reaches 1- V_{PP} peak and is more than enough to cause the output current to increase to its maximum value (see Figure 64 and Figure 65 plots).

NOTE

Because of the larger output sinking current compared to the sourcing one, the output negative transition is faster than the positive one.




Figure 66. Buffer Amplifier Scope Photo

24

Submit Documentation Feedback



9 Application and Implementation

NOTE

Information in the following applications sections is not part of the TI component specification, and TI does not warrant its accuracy or completeness. TI's customers are responsible for determining suitability of components for their purposes. Customers should validate and test their design implementation to confirm system functionality.

9.1 Application Information

9.1.1 Similar High-Output Devices

The LM7332 is a dual rail-to-rail amplifier with a slightly lower GBW capable of sinking and sourcing 100 mA. It is available in SOIC and VSSOP packages.

The LM4562 is dual op amp with very low noise and 0.7-mV voltage offset.

The LME49870 and LME49860 are single and dual low-noise amplifiers that can work from ±22-V supplies.

9.1.2 Other High Performance SOT-23 Ampliers

The LM7341 is a 4-MHz rail-to-rail input and output part that requires only 0.6 mA to operate, and can drive unlimited capacitive load. It has a voltage gain of 97 dB, a CMRR of 93 dB, and a PSRR of 104 dB.

The LM6211 is a 20-MHz part with CMOS input, which runs on ±12-V or 24-V single supplies. It has rail-to-rail output and low noise.

The LM7121 has a gain bandwidth of 235 MHz.

Detailed information on these parts can be found at www.ti.com.

9.2 Typical Application

Figure 67 shows a typical application where the LM732xx is used as a buffer amplifier for the V_{COM} signal employed in a TFT LCD flat panel:




Figure 67. V_{COM} Driver Application Schematic

9.2.1 Design Requirements

For this example application, the supply voltage is +5 V, and noninverting gain is necessary.



Typical Application (continued)

9.2.2 Detailed Design Procedure

Figure 68 shows the time domain response of the amplifier when used as a V_{COM} buffer/driver with V_{REF} at ground. In this application, the op amp loop will try and maintain its output voltage based on the voltage on its noninverting input (V_{REF}) despite the current injected into the TFT simulated load. As long as this load current is within the range tolerable by the LM732xx (45-mA sourcing and 65-mA sinking for ± 5 -V supplies), the output will settle to its final value within less than 2 μ s.




Figure 68. V_{COM} Driver Performance Scope Photo

9.2.3 Application Curve




Figure 69. Crosstalk Rejection vs. Frequency

S Submit Documentation Feedback



10 Power Supply Recommendations

The use of supply decoupling is mandatory in most applications. As with most relatively high-speed or high-output current op amps, best results are achieved when each supply line is decoupled with two capacitors; a small value ceramic capacitor (about $0.01~\mu F$) placed very close to the supply lead in addition to a large value Tantalum or Aluminum (> $4.7~\mu F$). The large capacitor can be shared by more than one device if necessary. The small ceramic capacitor maintains low supply impedance at high frequencies while the large capacitor will act as the charge *bucket* for fast load current spikes at the op amp output. The combination of these capacitors will provide supply decoupling and will help keep the op amp oscillation free under any load.

11 Layout

11.1 Layout Guidelines

Take care to minimize the loop area formed by the bypass capacitor connection between supply pins and ground. A ground plane underneath the device is recommended; any bypass components to ground should have a nearby via to the ground plane. The optimum bypass capacitor placement is closest to the corresponding supply pin. Use of thicker traces from the bypass capacitors to the corresponding supply pins will lower the power supply inductance and provide a more stable power supply.

The feedback components should be placed as close to the device as possible to minimize stray parasitics.

11.2 Layout Example




Figure 70. LM732xx Layout Example



12 Device and Documentation Support

12.1 Related Links

The table below lists quick access links. Categories include technical documents, support and community resources, tools and software, and quick access to sample or buy.

Table 2. Related Links

PARTS	PRODUCT FOLDER	SAMPLE & BUY	TECHNICAL DOCUMENTS	TOOLS & SOFTWARE	SUPPORT & COMMUNITY
LM7321	Click here	Click here	Click here	Click here	Click here
LM7322	Click here	Click here	Click here	Click here	Click here

12.2 Community Resources

The following links connect to TI community resources. Linked contents are provided "AS IS" by the respective contributors. They do not constitute TI specifications and do not necessarily reflect TI's views; see TI's Terms of Use.

TI E2E™ Online Community TI's Engineer-to-Engineer (E2E) Community. Created to foster collaboration among engineers. At e2e.ti.com, you can ask questions, share knowledge, explore ideas and help solve problems with fellow engineers.

Design Support *TI's Design Support* Quickly find helpful E2E forums along with design support tools and contact information for technical support.

12.3 Trademarks

E2E is a trademark of Texas Instruments.

All other trademarks are the property of their respective owners.

12.4 Electrostatic Discharge Caution



These devices have limited built-in ESD protection. The leads should be shorted together or the device placed in conductive foam during storage or handling to prevent electrostatic damage to the MOS gates.

12.5 Glossary

SLYZ022 — TI Glossary.

This glossary lists and explains terms, acronyms, and definitions.

13 Mechanical, Packaging, and Orderable Information

The following pages include mechanical, packaging, and orderable information. This information is the most current data available for the designated devices. This data is subject to change without notice and revision of this document. For browser-based versions of this data sheet, refer to the left-hand navigation.

Submit Documentation Feedback





29-Aug-2015

PACKAGING INFORMATION

Orderable Device	Status	Package Type	Package Drawing	Pins	Package Qty	Eco Plan	Lead/Ball Finish	MSL Peak Temp	Op Temp (°C)	Device Marking	Samples
LM7321MA/NOPB	ACTIVE	SOIC	D	8	95	Green (RoHS & no Sb/Br)	CU SN	Level-1-260C-UNLIM	-40 to 125	LM732 1MA	Samples
LM7321MAX/NOPB	ACTIVE	SOIC	D	8	2500	Green (RoHS & no Sb/Br)	CU SN	Level-1-260C-UNLIM	-40 to 125	LM732 1MA	Samples
LM7321MF/NOPB	ACTIVE	SOT-23	DBV	5	1000	Green (RoHS & no Sb/Br)	CU SN	Level-1-260C-UNLIM	-40 to 125	AU4A	Samples
LM7321MFE/NOPB	ACTIVE	SOT-23	DBV	5	250	Green (RoHS & no Sb/Br)	CU SN	Level-1-260C-UNLIM	-40 to 125	AU4A	Samples
LM7321MFX/NOPB	ACTIVE	SOT-23	DBV	5	3000	Green (RoHS & no Sb/Br)	CU SN	Level-1-260C-UNLIM	-40 to 125	AU4A	Samples
LM7321QMF/NOPB	ACTIVE	SOT-23	DBV	5	1000	Green (RoHS & no Sb/Br)	CU SN	Level-1-260C-UNLIM	-40 to 125	AR8A	Samples
LM7321QMFE/NOPB	ACTIVE	SOT-23	DBV	5	250	Green (RoHS & no Sb/Br)	CU SN	Level-1-260C-UNLIM	-40 to 125	AR8A	Samples
LM7321QMFX/NOPB	ACTIVE	SOT-23	DBV	5	3000	Green (RoHS & no Sb/Br)	CU SN	Level-1-260C-UNLIM	-40 to 125	AR8A	Samples
LM7322MA/NOPB	ACTIVE	SOIC	D	8	95	Green (RoHS & no Sb/Br)	CU SN	Level-1-260C-UNLIM	-40 to 125	LM732 2MA	Samples
LM7322MAX/NOPB	ACTIVE	SOIC	D	8	2500	Green (RoHS & no Sb/Br)	CU SN	Level-1-260C-UNLIM	-40 to 125	LM732 2MA	Samples
LM7322MM/NOPB	ACTIVE	VSSOP	DGK	8	1000	Green (RoHS & no Sb/Br)	CU SN	Level-1-260C-UNLIM	-40 to 125	AZ4A	Samples
LM7322MME/NOPB	ACTIVE	VSSOP	DGK	8	250	Green (RoHS & no Sb/Br)	CU SN	Level-1-260C-UNLIM	-40 to 125	AZ4A	Samples
LM7322MMX/NOPB	ACTIVE	VSSOP	DGK	8		TBD	Call TI	Call TI	-40 to 125	AZ4A	Samples
LM7322QMA/NOPB	ACTIVE	SOIC	D	8	95	Green (RoHS & no Sb/Br)	CU SN	Level-1-260C-UNLIM	-40 to 125	LM732 2QMA	Samples
LM7322QMAX/NOPB	ACTIVE	SOIC	D	8	2500	Green (RoHS & no Sb/Br)	CU SN	Level-1-260C-UNLIM	-40 to 125	LM732 2QMA	Samples

⁽¹⁾ The marketing status values are defined as follows: **ACTIVE:** Product device recommended for new designs.

LIFEBUY: TI has announced that the device will be discontinued, and a lifetime-buy period is in effect.

NRND: Not recommended for new designs. Device is in production to support existing customers, but TI does not recommend using this part in a new design.

PREVIEW: Device has been announced but is not in production. Samples may or may not be available.

PACKAGE OPTION ADDENDUM



29-Aug-2015

OBSOLETE: TI has discontinued the production of the device.

(2) Eco Plan - The planned eco-friendly classification: Pb-Free (RoHS), Pb-Free (RoHS Exempt), or Green (RoHS & no Sb/Br) - please check http://www.ti.com/productcontent for the latest availability information and additional product content details.

TBD: The Pb-Free/Green conversion plan has not been defined.

Pb-Free (RoHS): TI's terms "Lead-Free" or "Pb-Free" mean semiconductor products that are compatible with the current RoHS requirements for all 6 substances, including the requirement that lead not exceed 0.1% by weight in homogeneous materials. Where designed to be soldered at high temperatures, TI Pb-Free products are suitable for use in specified lead-free processes. **Pb-Free** (RoHS Exempt): This component has a RoHS exemption for either 1) lead-based flip-chip solder bumps used between the die and package, or 2) lead-based die adhesive used between the die and leadframe. The component is otherwise considered Pb-Free (RoHS compatible) as defined above.

Green (RoHS & no Sb/Br): TI defines "Green" to mean Pb-Free (RoHS compatible), and free of Bromine (Br) and Antimony (Sb) based flame retardants (Br or Sb do not exceed 0.1% by weight in homogeneous material)

- (3) MSL, Peak Temp. The Moisture Sensitivity Level rating according to the JEDEC industry standard classifications, and peak solder temperature.
- (4) There may be additional marking, which relates to the logo, the lot trace code information, or the environmental category on the device.
- (5) Multiple Device Markings will be inside parentheses. Only one Device Marking contained in parentheses and separated by a "~" will appear on a device. If a line is indented then it is a continuation of the previous line and the two combined represent the entire Device Marking for that device.
- (6) Lead/Ball Finish Orderable Devices may have multiple material finish options. Finish options are separated by a vertical ruled line. Lead/Ball Finish values may wrap to two lines if the finish value exceeds the maximum column width.

Important Information and Disclaimer: The information provided on this page represents TI's knowledge and belief as of the date that it is provided. TI bases its knowledge and belief on information provided by third parties, and makes no representation or warranty as to the accuracy of such information. Efforts are underway to better integrate information from third parties. TI has taken and continues to take reasonable steps to provide representative and accurate information but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals. TI and TI suppliers consider certain information to be proprietary, and thus CAS numbers and other limited information may not be available for release.

In no event shall TI's liability arising out of such information exceed the total purchase price of the TI part(s) at issue in this document sold by TI to Customer on an annual basis.

OTHER QUALIFIED VERSIONS OF LM7321, LM7321-Q1, LM7322, LM7322-Q1:

Catalog: LM7321, LM7322

Automotive: LM7321-Q1, LM7322-Q1

NOTE: Qualified Version Definitions:

Catalog - TI's standard catalog product



PACKAGE OPTION ADDENDUM

29-Aug-2015

• Automotive - Q100 devices qualified for high-reliability automotive applications targeting zero defects

PACKAGE MATERIALS INFORMATION

www.ti.com 2-Sep-2015


TAPE AND REEL INFORMATION





	Dimension designed to accommodate the component width
	Dimension designed to accommodate the component length
K0	Dimension designed to accommodate the component thickness
W	Overall width of the carrier tape
P1	Pitch between successive cavity centers

QUADRANT ASSIGNMENTS FOR PIN 1 ORIENTATION IN TAPE



*All dimensions are nominal

Device	Package Type	Package Drawing		SPQ	Reel Diameter (mm)	Reel Width W1 (mm)	A0 (mm)	B0 (mm)	K0 (mm)	P1 (mm)	W (mm)	Pin1 Quadrant
LM7321MAX/NOPB	SOIC	D	8	2500	330.0	12.4	6.5	5.4	2.0	8.0	12.0	Q1
LM7321MF/NOPB	SOT-23	DBV	5	1000	178.0	8.4	3.2	3.2	1.4	4.0	8.0	Q3
LM7321MFE/NOPB	SOT-23	DBV	5	250	178.0	8.4	3.2	3.2	1.4	4.0	8.0	Q3
LM7321MFX/NOPB	SOT-23	DBV	5	3000	178.0	8.4	3.2	3.2	1.4	4.0	8.0	Q3
LM7321QMF/NOPB	SOT-23	DBV	5	1000	178.0	8.4	3.2	3.2	1.4	4.0	8.0	Q3
LM7321QMFE/NOPB	SOT-23	DBV	5	250	178.0	8.4	3.2	3.2	1.4	4.0	8.0	Q3
LM7321QMFX/NOPB	SOT-23	DBV	5	3000	178.0	8.4	3.2	3.2	1.4	4.0	8.0	Q3
LM7322MAX/NOPB	SOIC	D	8	2500	330.0	12.4	6.5	5.4	2.0	8.0	12.0	Q1
LM7322MM/NOPB	VSSOP	DGK	8	1000	178.0	12.4	5.3	3.4	1.4	8.0	12.0	Q1
LM7322MME/NOPB	VSSOP	DGK	8	250	178.0	12.4	5.3	3.4	1.4	8.0	12.0	Q1
LM7322QMAX/NOPB	SOIC	D	8	2500	330.0	12.4	6.5	5.4	2.0	8.0	12.0	Q1

www.ti.com 2-Sep-2015



*All dimensions are nominal

All dimensions are nominal							
Device	Package Type	Package Drawing	Pins	SPQ	Length (mm)	Width (mm)	Height (mm)
LM7321MAX/NOPB	SOIC	D	8	2500	367.0	367.0	35.0
LM7321MF/NOPB	SOT-23	DBV	5	1000	210.0	185.0	35.0
LM7321MFE/NOPB	SOT-23	DBV	5	250	210.0	185.0	35.0
LM7321MFX/NOPB	SOT-23	DBV	5	3000	210.0	185.0	35.0
LM7321QMF/NOPB	SOT-23	DBV	5	1000	210.0	185.0	35.0
LM7321QMFE/NOPB	SOT-23	DBV	5	250	210.0	185.0	35.0
LM7321QMFX/NOPB	SOT-23	DBV	5	3000	210.0	185.0	35.0
LM7322MAX/NOPB	SOIC	D	8	2500	367.0	367.0	35.0
LM7322MM/NOPB	VSSOP	DGK	8	1000	210.0	185.0	35.0
LM7322MME/NOPB	VSSOP	DGK	8	250	210.0	185.0	35.0
LM7322QMAX/NOPB	SOIC	D	8	2500	367.0	367.0	35.0

DBV (R-PDSO-G5)

PLASTIC SMALL-OUTLINE PACKAGE



- A. All linear dimensions are in millimeters.
- B. This drawing is subject to change without notice.
- C. Body dimensions do not include mold flash or protrusion. Mold flash and protrusion shall not exceed 0.15 per side.
- D. Falls within JEDEC MO-178 Variation AA.



DBV (R-PDSO-G5)

PLASTIC SMALL OUTLINE



- A. All linear dimensions are in millimeters.
- B. This drawing is subject to change without notice.
- C. Customers should place a note on the circuit board fabrication drawing not to alter the center solder mask defined pad.
- D. Publication IPC-7351 is recommended for alternate designs.
- E. Laser cutting apertures with trapezoidal walls and also rounding corners will offer better paste release. Customers should contact their board assembly site for stencil design recommendations. Example stencil design based on a 50% volumetric metal load solder paste. Refer to IPC-7525 for other stencil recommendations.



DGK (S-PDSO-G8)

PLASTIC SMALL-OUTLINE PACKAGE



- A. All linear dimensions are in millimeters.
- B. This drawing is subject to change without notice.
- Body length does not include mold flash, protrusions, or gate burrs. Mold flash, protrusions, or gate burrs shall not exceed 0.15 per end.
- Body width does not include interlead flash. Interlead flash shall not exceed 0.50 per side.
- E. Falls within JEDEC MO-187 variation AA, except interlead flash.



D (R-PDSO-G8)

PLASTIC SMALL OUTLINE



- A. All linear dimensions are in inches (millimeters).
- B. This drawing is subject to change without notice.
- Body length does not include mold flash, protrusions, or gate burrs. Mold flash, protrusions, or gate burrs shall not exceed 0.006 (0,15) each side.
- Body width does not include interlead flash. Interlead flash shall not exceed 0.017 (0,43) each side.
- E. Reference JEDEC MS-012 variation AA.



IMPORTANT NOTICE

Texas Instruments Incorporated and its subsidiaries (TI) reserve the right to make corrections, enhancements, improvements and other changes to its semiconductor products and services per JESD46, latest issue, and to discontinue any product or service per JESD48, latest issue. Buyers should obtain the latest relevant information before placing orders and should verify that such information is current and complete. All semiconductor products (also referred to herein as "components") are sold subject to TI's terms and conditions of sale supplied at the time of order acknowledgment.

TI warrants performance of its components to the specifications applicable at the time of sale, in accordance with the warranty in TI's terms and conditions of sale of semiconductor products. Testing and other quality control techniques are used to the extent TI deems necessary to support this warranty. Except where mandated by applicable law, testing of all parameters of each component is not necessarily performed.

TI assumes no liability for applications assistance or the design of Buyers' products. Buyers are responsible for their products and applications using TI components. To minimize the risks associated with Buyers' products and applications, Buyers should provide adequate design and operating safeguards.

TI does not warrant or represent that any license, either express or implied, is granted under any patent right, copyright, mask work right, or other intellectual property right relating to any combination, machine, or process in which TI components or services are used. Information published by TI regarding third-party products or services does not constitute a license to use such products or services or a warranty or endorsement thereof. Use of such information may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

Reproduction of significant portions of TI information in TI data books or data sheets is permissible only if reproduction is without alteration and is accompanied by all associated warranties, conditions, limitations, and notices. TI is not responsible or liable for such altered documentation. Information of third parties may be subject to additional restrictions.

Resale of TI components or services with statements different from or beyond the parameters stated by TI for that component or service voids all express and any implied warranties for the associated TI component or service and is an unfair and deceptive business practice. TI is not responsible or liable for any such statements.

Buyer acknowledges and agrees that it is solely responsible for compliance with all legal, regulatory and safety-related requirements concerning its products, and any use of TI components in its applications, notwithstanding any applications-related information or support that may be provided by TI. Buyer represents and agrees that it has all the necessary expertise to create and implement safeguards which anticipate dangerous consequences of failures, monitor failures and their consequences, lessen the likelihood of failures that might cause harm and take appropriate remedial actions. Buyer will fully indemnify TI and its representatives against any damages arising out of the use of any TI components in safety-critical applications.

In some cases, TI components may be promoted specifically to facilitate safety-related applications. With such components, TI's goal is to help enable customers to design and create their own end-product solutions that meet applicable functional safety standards and requirements. Nonetheless, such components are subject to these terms.

No TI components are authorized for use in FDA Class III (or similar life-critical medical equipment) unless authorized officers of the parties have executed a special agreement specifically governing such use.

Only those TI components which TI has specifically designated as military grade or "enhanced plastic" are designed and intended for use in military/aerospace applications or environments. Buyer acknowledges and agrees that any military or aerospace use of TI components which have not been so designated is solely at the Buyer's risk, and that Buyer is solely responsible for compliance with all legal and regulatory requirements in connection with such use.

TI has specifically designated certain components as meeting ISO/TS16949 requirements, mainly for automotive use. In any case of use of non-designated products, TI will not be responsible for any failure to meet ISO/TS16949.

Products Applications

logic.ti.com

Audio www.ti.com/audio Automotive and Transportation www.ti.com/automotive **Amplifiers** amplifier.ti.com Communications and Telecom www.ti.com/communications **Data Converters** dataconverter.ti.com Computers and Peripherals www.ti.com/computers **DLP® Products** www.dlp.com Consumer Electronics www.ti.com/consumer-apps DSP dsp.ti.com **Energy and Lighting** www.ti.com/energy Clocks and Timers www.ti.com/clocks Industrial www.ti.com/industrial Interface interface.ti.com Medical www.ti.com/medical Logic Security www.ti.com/security

Power Mgmt Space, Avionics and Defense www.ti.com/space-avionics-defense power.ti.com

Microcontrollers www.ti.com/video microcontroller.ti.com Video and Imaging

www.ti-rfid.com

OMAP Applications Processors TI E2E Community www.ti.com/omap e2e.ti.com

Wireless Connectivity www.ti.com/wirelessconnectivity