

Stellaris® LM4F232H5QC Microcontroller

DATA SHEET

Copyright

Copyright © 2007-2013 Texas Instruments Incorporated All rights reserved. Stellaris and StellarisWare® are registered trademarks of Texas Instruments Incorporated. ARM and Thumb are registered trademarks and Cortex is a trademark of ARM Limited. Other names and brands may be claimed as the property of others.

ADVANCE INFORMATION concerns new products in the sampling or preproduction phase of development. Characteristic data and other specifications are subject to change without notice.

A Please be aware that an important notice concerning availability, standard warranty, and use in critical applications of Texas Instruments semiconductor products and disclaimers thereto appears at the end of this data sheet.

Texas Instruments Incorporated 108 Wild Basin, Suite 350 Austin, TX 78746 http://www.ti.com/stellaris







http://www-k.ext.ti.com/sc/technical-support/product-information-centers.htm

Table of Contents

Revision His	story	38
About This I	Document	46
Audience		46
About This Ma	anual	46
Related Docur	ments	46
Documentation	n Conventions	47
1	Architectural Overview	49
1.1	Series Overview	49
1.2	LM4F232H5QC Microcontroller Overview	50
1.3	LM4F232H5QC Microcontroller Features	53
1.3.1	ARM Cortex-M4F Processor Core	53
1.3.2	On-Chip Memory	55
1.3.3	Serial Communications Peripherals	
1.3.4	System Integration	61
1.3.5	Advanced Motion Control	67
1.3.6	Analog	69
1.3.7	JTAG and ARM Serial Wire Debug	71
1.3.8	Packaging and Temperature	72
1.4	LM4F232H5QC Microcontroller Hardware Details	72
2	The Cortex-M4F Processor	73
_ 2.1	Block Diagram	
2.2	Overview	
2.2.1	System-Level Interface	75
2.2.2	Integrated Configurable Debug	
2.2.3	Trace Port Interface Unit (TPIU)	
2.2.4	Cortex-M4F System Component Details	
2.3	Programming Model	
2.3.1	Processor Mode and Privilege Levels for Software Execution	
2.3.2	Stacks	78
2.3.3	Register Map	78
2.3.4	Register Descriptions	
2.3.5	Exceptions and Interrupts	96
2.3.6	Data Types	96
2.4	Memory Model	96
2.4.1	Memory Regions, Types and Attributes	99
2.4.2	Memory System Ordering of Memory Accesses	99
2.4.3	Behavior of Memory Accesses	99
2.4.4	Software Ordering of Memory Accesses	100
2.4.5	Bit-Banding	101
2.4.6	Data Storage	103
2.4.7	Synchronization Primitives	104
2.5	Exception Model	105
2.5.1	Exception States	106
2.5.2	Exception Types	106
2.5.3	Exception Handlers	110

2.5.4	Vector Table	111
2.5.5	Exception Priorities	111
2.5.6	Interrupt Priority Grouping	112
2.5.7	Exception Entry and Return	112
2.6	Fault Handling	115
2.6.1	Fault Types	116
2.6.2	Fault Escalation and Hard Faults	116
2.6.3	Fault Status Registers and Fault Address Registers	117
2.6.4	Lockup	
2.7	Power Management	118
2.7.1	Entering Sleep Modes	
2.7.2	Wake Up from Sleep Mode	
2.8	Instruction Set Summary	
3	Cortex-M4 Peripherals	
3.1	Functional Description	
3.1.1	System Timer (SysTick)	
3.1.2	Nested Vectored Interrupt Controller (NVIC)	
3.1.3	System Control Block (SCB)	
3.1.4	Memory Protection Unit (MPU)	
3.1.5	Floating-Point Unit (FPU)	
3.1.3	Register Map	
3.3	System Timer (SysTick) Register Descriptions	
3.4	NVIC Register Descriptions	
3.5	System Control Block (SCB) Register Descriptions	
3.6	· · · · · · · · · · · · · · · · · · ·	
3.7	Memory Protection Unit (MPU) Register Descriptions	
4	JTAG Interface	
4.1	Block Diagram	
4.2	Signal Description	
4.3	Functional Description	
4.3.1	JTAG Interface Pins	
4.3.2	JTAG TAP Controller	
4.3.3	Shift Registers	
4.3.4	Operational Considerations	
4.4	Initialization and Configuration	
4.5	Register Descriptions	
4.5.1	Instruction Register (IR)	
4.5.2	Data Registers	
5	System Control	216
5.1	Signal Description	216
5.2	Functional Description	
5.2.1	Device Identification	
5.2.2	Reset Control	
5.2.3	Non-Maskable Interrupt	
5.2.4	Power Control	
5.2.5	Clock Control	223
5.2.6	System Control	231
5.3	Initialization and Configuration	

5.4	Register Map	234
5.5	System Control Register Descriptions	239
5.6	System Control Legacy Register Descriptions	417
6	System Exception Module	483
6.1	Functional Description	
6.2	Register Map	483
6.3	Register Descriptions	483
7	Hibernation Module	491
7.1	Block Diagram	
7.2	Signal Description	
7.3	Functional Description	493
7.3.1	Register Access Timing	493
7.3.2	Hibernation Clock Source	494
7.3.3	System Implementation	495
7.3.4	Battery Management	496
7.3.5	Real-Time Clock	497
7.3.6	Battery-Backed Memory	499
7.3.7	Power Control Using HIB	499
7.3.8	Power Control Using VDD3ON Mode	499
7.3.9	Initiating Hibernate	499
7.3.10	Waking from Hibernate	500
7.3.11	Arbitrary Power Removal	500
7.3.12	Interrupts and Status	500
7.4	Initialization and Configuration	501
7.4.1	Initialization	501
7.4.2	RTC Match Functionality (No Hibernation)	502
7.4.3	RTC Match/Wake-Up from Hibernation	502
7.4.4	External Wake-Up from Hibernation	502
7.4.5	RTC or External Wake-Up from Hibernation	503
7.5	Register Map	503
7.6	Register Descriptions	504
8	Internal Memory	522
8.1	Block Diagram	
8.2	Functional Description	523
8.2.1	SRAM	523
8.2.2	ROM	524
8.2.3	Flash Memory	526
8.2.4	EEPROM	531
8.3	Register Map	537
8.4	Flash Memory Register Descriptions (Flash Control Offset)	538
8.5	EEPROM Register Descriptions (EEPROM Offset)	556
8.6	Memory Register Descriptions (System Control Offset)	573
9	Micro Direct Memory Access (µDMA)	582
9.1	Block Diagram	
9.2	Functional Description	
9.2.1	Channel Assignments	
9.2.2	Priority	585

9.2.3	Arbitration Size	585
9.2.4	Request Types	585
9.2.5	Channel Configuration	586
9.2.6	Transfer Modes	588
9.2.7	Transfer Size and Increment	596
9.2.8	Peripheral Interface	596
9.2.9	Software Request	596
9.2.10	Interrupts and Errors	597
9.3	Initialization and Configuration	
9.3.1	Module Initialization	
9.3.2	Configuring a Memory-to-Memory Transfer	598
9.3.3	Configuring a Peripheral for Simple Transmit	
9.3.4	Configuring a Peripheral for Ping-Pong Receive	
9.3.5	Configuring Channel Assignments	
9.4	Register Map	
9.5	μDMA Channel Control Structure	
9.6	μDMA Register Descriptions	
10	General-Purpose Input/Outputs (GPIOs)	
10.1	Signal Description	
10.1	Functional Description	
10.2.1	Data Control	
10.2.1	Interrupt Control	
10.2.2	Mode Control	
10.2.3		
10.2.4	Pad Control	
10.2.5	Identification	
10.2.0	Initialization and Configuration	
10.3	Register Map	
10.4	Register Descriptions	
	-	
11	General-Purpose Timers	
11.1	Block Diagram	
11.2	Signal Description	
11.3	Functional Description	
11.3.1	GPTM Reset Conditions	
11.3.2	Timer Modes	
11.3.3	Wait-for-Trigger Mode	
11.3.4	Synchronizing GP Timer Blocks	
11.3.5	DMA Operation	
11.3.6	Accessing Concatenated 16/32-Bit GPTM Register Values	
11.3.7	Accessing Concatenated 32/64-Bit Wide GPTM Register Values	
11.4	Initialization and Configuration	
11.4.1	One-Shot/Periodic Timer Mode	722
11.4.2	Real-Time Clock (RTC) Mode	
11.4.3	Input Edge-Count Mode	
11.4.4	Input Edge Timing Mode	724
11.4.5	PWM Mode	724
11.5	Register Map	725
11.6	Register Descriptions	726

12	Watchdog Timers	774
12.1	Block Diagram	775
12.2	Functional Description	775
12.2.1	Register Access Timing	776
12.3	Initialization and Configuration	
12.4	Register Map	
12.5	Register Descriptions	
13	Analog-to-Digital Converter (ADC)	
13.1	Block Diagram	
13.2	Signal Description	
13.3	Functional Description	
13.3.1	Sample Sequencers	
13.3.2	Module Control	
	Hardware Sample Averaging Circuit	
	Analog-to-Digital Converter	
	Differential Sampling	
	Internal Temperature Sensor	
13.3.7	·	
	Digital Comparator Unit	
13.4	· · · · · · · · · · · · · · · · · · ·	
13.4.1	Module Initialization	
13.4.2	Sample Sequencer Configuration	
13.5	Register Map	
13.6	Register Descriptions	
14	Universal Asynchronous Receivers/Transmitters (UARTs)	
14.1	Block Diagram	
14.2	Signal Description	
14.3	Functional Description	
14.3.1	Transmit/Receive Logic	
	Baud-Rate Generation	
	Data Transmission	
14.3.4	Serial IR (SIR)	902
14.3.5	ISO 7816 Support	904
14.3.6	Modem Handshake Support	904
14.3.7	9-Bit UART Mode	905
14.3.8	FIFO Operation	906
14.3.9	Interrupts	906
14.3.10	Loopback Operation	907
14.3.11	DMA Operation	907
14.4	Initialization and Configuration	908
14.5	Register Map	909
14.6	Register Descriptions	910
15	Synchronous Serial Interface (SSI)	958
15.1	Block Diagram	
15.2	Signal Description	
15.3	Functional Description	
	Bit Rate Generation	
	FIFO Operation	
	Interrupts	
	p	

15.3.4	Frame Formats	962
15.3.5	DMA Operation	970
15.4	Initialization and Configuration	970
15.5	Register Map	972
15.6	Register Descriptions	973
16	Inter-Integrated Circuit (I ² C) Interface	1002
16.1	Block Diagram	1003
16.2	Signal Description	1003
16.3	Functional Description	1004
16.3.1	I ² C Bus Functional Overview	1004
16.3.2	Available Speed Modes	1008
16.3.3	Interrupts	1010
16.3.4	Loopback Operation	1011
16.3.5	Command Sequence Flow Charts	1012
16.4	Initialization and Configuration	1020
16.5	Register Map	
16.6	Register Descriptions (I ² C Master)	1023
16.7	Register Descriptions (I ² C Slave)	1040
16.8	Register Descriptions (I ² C Status and Control)	1050
17	Controller Area Network (CAN) Module	1053
17.1	Block Diagram	
17.2	Signal Description	1054
17.3	Functional Description	1055
17.3.1	Initialization	1056
17.3.2	Operation	1057
17.3.3	Transmitting Message Objects	1058
17.3.4	Configuring a Transmit Message Object	1058
17.3.5	Updating a Transmit Message Object	1059
	Accepting Received Message Objects	
	Receiving a Data Frame	
	Receiving a Remote Frame	
	Receive/Transmit Priority	
	Configuring a Receive Message Object	
	Handling of Received Message Objects	
	Handling of Interrupts	
	Test Mode	
	Bit Timing Configuration Error Considerations	
	Bit Time and Bit Rate	
	Calculating the Bit Timing Parameters	
17.4	Register Map	
17.5	CAN Register Descriptions	
18	Universal Serial Bus (USB) Controller	
18.1	Block Diagram	
18.2	Signal Description	
18.3	Functional Description	
18.3.1	Operation as a Device	
1832	Operation as a Host	1111

18.3.3	OTG Mode	1115
18.3.4	DMA Operation	
18.4	Initialization and Configuration	
18.4.1	Pin Configuration	
18.4.2	Endpoint Configuration	
18.5	Register Map	
18.6	Register Descriptions	1125
19	Analog Comparators	
19.1	Block Diagram	
19.2	Signal Description	
19.3	Functional Description	
19.3.1	Internal Reference Programming	
19.4	Initialization and Configuration	
19.5	Register Map	
19.6	Register Descriptions	
20	Pulse Width Modulator (PWM)	
20.1	Block Diagram	
20.2	Signal Description	
20.3	Functional Description	
20.3.1	PWM Timer	
	PWM Comparators	
	PWM Signal Generator	
	Dead-Band Generator	
	Interrupt/ADC-Trigger Selector	
	Synchronization Methods	
	Fault Conditions	
20.3.8	Output Control Block	
20.4	Initialization and Configuration	
20.5	Register Map	
20.6	Register Descriptions	
21	Quadrature Encoder Interface (QEI)	
21.1	Block Diagram	
21.2	Signal Description	
21.3	Functional Description	
21.4	Initialization and Configuration	
21.5	Register Map	
21.6	Register Descriptions	
22	Pin Diagram	
23	Signal Tables	
23.1	Signals by Pin Number	
23.2	Signals by Signal Name	
23.3	Signals by Function, Except for GPIO	
23.4	GPIO Pins and Alternate Functions	
23.5	Possible Pin Assignments for Alternate Functions	
23.6	Connections for Unused Signals	1374
24	Electrical Characteristics	
24.1	Operating Characteristics	1376

24.2	Maximum Ratings	1377
24.3	Recommended Operating Conditions	1378
24.4	Load Conditions	1380
24.5	JTAG and Boundary Scan	1381
24.6	Power and Brown-Out	1383
24.6.1	VDDA Levels	1383
24.6.2	VDD Levels	1384
24.6.3	VDDC Levels	1385
24.6.4	VDD Glitches	1386
24.6.5	VDD Droop Response	1386
24.7	Reset	1388
24.8	On-Chip Low Drop-Out (LDO) Regulator	1390
24.9	Clocks	1391
24.9.1	PLL Specifications	1391
24.9.2	PIOSC Specifications	1392
24.9.3	Low-Frequency Internal Oscillator (LFIOSC) Specifications	1392
24.9.4	Hibernation Clock Source Specifications	1392
24.9.5	Main Oscillator Specifications	1393
24.9.6	System Clock Specification with ADC Operation	1396
24.9.7	System Clock Specification with USB Operation	1396
24.10	Sleep Modes	1397
24.11	Hibernation Module	1398
24.12	Flash Memory and EEPROM	1399
24.13	Input/Output Pin Characteristics	1400
24.13.1	GPIO Module Characteristics	1400
24.13.2	Types of I/O Pins and ESD Protection	1400
24.14	Analog-to-Digital Converter (ADC)	1403
24.15	Synchronous Serial Interface (SSI)	1407
24.16	Inter-Integrated Circuit (I ² C) Interface	1409
24.17	Universal Serial Bus (USB) Controller	1410
24.18	Analog Comparator	1411
24.19	Current Consumption	1413
24.19.1	Preliminary Current Consumption	1413
Α	Ordering and Contact Information	1415
A.1	Ordering Information	
A.2	Part Markings	
A.3	Kits	1415
A.4	Support Information	1416
В	Package Information	1417
B.1	100-Pin LQFP Package	
B.1.1	Package Dimensions	
	-	

11

List of Figures

Figure 1-1.	Stellaris® Blizzard-class Block Diagram	50
Figure 1-2.	Stellaris LM4F232H5QC Microcontroller High-Level Block Diagram	52
Figure 2-1.	CPU Block Diagram	
Figure 2-2.	TPIU Block Diagram	
Figure 2-3.	Cortex-M4F Register Set	
Figure 2-4.	Bit-Band Mapping	
Figure 2-5.	Data Storage	104
Figure 2-6.	Vector Table	
Figure 2-7.	Exception Stack Frame	114
Figure 3-1.	SRD Use Example	132
Figure 3-2.	FPU Register Bank	135
Figure 4-1.	JTAG Module Block Diagram	205
Figure 4-2.	Test Access Port State Machine	208
Figure 4-3.	IDCODE Register Format	214
Figure 4-4.	BYPASS Register Format	214
Figure 4-5.	Boundary Scan Register Format	
Figure 5-1.	Basic RST Configuration	
Figure 5-2.	External Circuitry to Extend Power-On Reset	
Figure 5-3.	Reset Circuit Controlled by Switch	
Figure 5-4.	Power Architecture	
Figure 5-5.	Main Clock Tree	226
Figure 5-6.	Module Clock Selection	233
Figure 7-1.	Hibernation Module Block Diagram	492
Figure 7-2.		494
•	Using a Crystal as the Hibernation Clock Source with a Single Battery Source Using a Dedicated Oscillator as the Hibernation Clock Source with VDD3ON	494
Figure 7-2.	Using a Crystal as the Hibernation Clock Source with a Single Battery Source	
Figure 7-2.	Using a Crystal as the Hibernation Clock Source with a Single Battery Source Using a Dedicated Oscillator as the Hibernation Clock Source with VDD3ON	495
Figure 7-2. Figure 7-3.	Using a Crystal as the Hibernation Clock Source with a Single Battery Source Using a Dedicated Oscillator as the Hibernation Clock Source with VDD3ON Mode	495 496
Figure 7-2. Figure 7-3. Figure 7-4.	Using a Crystal as the Hibernation Clock Source with a Single Battery Source Using a Dedicated Oscillator as the Hibernation Clock Source with VDD3ON Mode Using a Regulator for Both V_{DD} and V_{BAT}	495 496 522
Figure 7-2. Figure 7-3. Figure 7-4. Figure 8-1.	Using a Crystal as the Hibernation Clock Source with a Single Battery Source Using a Dedicated Oscillator as the Hibernation Clock Source with VDD3ON Mode	495 496 522 523
Figure 7-2. Figure 7-3. Figure 7-4. Figure 8-1. Figure 8-2.	Using a Crystal as the Hibernation Clock Source with a Single Battery Source Using a Dedicated Oscillator as the Hibernation Clock Source with VDD3ON Mode Using a Regulator for Both V _{DD} and V _{BAT} Internal Memory Block Diagram EEPROM Block Diagram	495 496 522 523
Figure 7-2. Figure 7-3. Figure 7-4. Figure 8-1. Figure 8-2. Figure 9-1.	Using a Crystal as the Hibernation Clock Source with a Single Battery Source Using a Dedicated Oscillator as the Hibernation Clock Source with VDD3ON Mode Using a Regulator for Both V_{DD} and V_{BAT} Internal Memory Block Diagram EEPROM Block Diagram μ DMA Block Diagram	495 496 522 523 583
Figure 7-2. Figure 7-3. Figure 7-4. Figure 8-1. Figure 8-2. Figure 9-1. Figure 9-2.	Using a Crystal as the Hibernation Clock Source with a Single Battery Source Using a Dedicated Oscillator as the Hibernation Clock Source with VDD3ON Mode Using a Regulator for Both V _{DD} and V _{BAT} Internal Memory Block Diagram EEPROM Block Diagram µDMA Block Diagram Example of Ping-Pong µDMA Transaction	495 496 522 523 583 589
Figure 7-2. Figure 7-3. Figure 7-4. Figure 8-1. Figure 8-2. Figure 9-1. Figure 9-2. Figure 9-3.	Using a Crystal as the Hibernation Clock Source with a Single Battery Source Using a Dedicated Oscillator as the Hibernation Clock Source with VDD3ON Mode Using a Regulator for Both V_{DD} and V_{BAT} Internal Memory Block Diagram EEPROM Block Diagram μ DMA Block Diagram μ DMA Block Diagram Example of Ping-Pong μ DMA Transaction Memory Scatter-Gather, Setup and Configuration	495 496 522 583 589 591
Figure 7-2. Figure 7-3. Figure 8-1. Figure 8-2. Figure 9-1. Figure 9-2. Figure 9-3. Figure 9-4.	Using a Crystal as the Hibernation Clock Source with a Single Battery Source Using a Dedicated Oscillator as the Hibernation Clock Source with VDD3ON Mode Using a Regulator for Both V_{DD} and V_{BAT} Internal Memory Block Diagram EEPROM Block Diagram μ DMA Block Diagram Example of Ping-Pong μ DMA Transaction Memory Scatter-Gather, μ DMA Copy Sequence	495 496 522 523 583 589 591 592
Figure 7-2. Figure 7-3. Figure 8-1. Figure 8-2. Figure 9-1. Figure 9-2. Figure 9-3. Figure 9-4. Figure 9-5.	Using a Crystal as the Hibernation Clock Source with a Single Battery Source Using a Dedicated Oscillator as the Hibernation Clock Source with VDD3ON Mode Using a Regulator for Both V_{DD} and V_{BAT} Internal Memory Block Diagram EEPROM Block Diagram EEPROM Block Diagram Example of Ping-Pong μ DMA Transaction Memory Scatter-Gather, Setup and Configuration Memory Scatter-Gather, μ DMA Copy Sequence Peripheral Scatter-Gather, Setup and Configuration	495 496 522 523 583 589 591 592 594
Figure 7-2. Figure 7-3. Figure 7-4. Figure 8-1. Figure 8-2. Figure 9-1. Figure 9-2. Figure 9-3. Figure 9-4. Figure 9-5. Figure 9-6.	Using a Crystal as the Hibernation Clock Source with a Single Battery Source Using a Dedicated Oscillator as the Hibernation Clock Source with VDD3ON Mode Using a Regulator for Both V _{DD} and V _{BAT} Internal Memory Block Diagram EEPROM Block Diagram µDMA Block Diagram Example of Ping-Pong µDMA Transaction Memory Scatter-Gather, Setup and Configuration Memory Scatter-Gather, µDMA Copy Sequence Peripheral Scatter-Gather, µDMA Copy Sequence Peripheral Scatter-Gather, µDMA Copy Sequence	495 496 522 583 589 591 592 594 595
Figure 7-2. Figure 7-3. Figure 8-1. Figure 8-2. Figure 9-1. Figure 9-2. Figure 9-3. Figure 9-4. Figure 9-5. Figure 9-6. Figure 10-1.	Using a Crystal as the Hibernation Clock Source with a Single Battery Source Using a Dedicated Oscillator as the Hibernation Clock Source with VDD3ON Mode Using a Regulator for Both V _{DD} and V _{BAT} Internal Memory Block Diagram EEPROM Block Diagram µDMA Block Diagram Example of Ping-Pong µDMA Transaction Memory Scatter-Gather, Setup and Configuration Memory Scatter-Gather, µDMA Copy Sequence Peripheral Scatter-Gather, Setup and Configuration Peripheral Scatter-Gather, µDMA Copy Sequence Digital I/O Pads	495 496 522 523 589 591 592 594 595 650
Figure 7-2. Figure 7-3. Figure 8-1. Figure 8-2. Figure 9-1. Figure 9-2. Figure 9-3. Figure 9-4. Figure 9-5. Figure 9-6. Figure 10-1. Figure 10-2.	Using a Crystal as the Hibernation Clock Source with a Single Battery Source Using a Dedicated Oscillator as the Hibernation Clock Source with VDD3ON Mode Using a Regulator for Both V _{DD} and V _{BAT}	495 496 522 583 589 591 592 595 650 651
Figure 7-2. Figure 7-3. Figure 7-4. Figure 8-1. Figure 8-2. Figure 9-1. Figure 9-2. Figure 9-3. Figure 9-4. Figure 9-5. Figure 9-6. Figure 10-1. Figure 10-2. Figure 10-3.	Using a Crystal as the Hibernation Clock Source with a Single Battery Source Using a Dedicated Oscillator as the Hibernation Clock Source with VDD3ON Mode Using a Regulator for Both V _{DD} and V _{BAT} Internal Memory Block Diagram EEPROM Block Diagram EXAMPLE OF Ping-Pong µDMA Transaction Memory Scatter-Gather, Setup and Configuration Memory Scatter-Gather, µDMA Copy Sequence Peripheral Scatter-Gather, Setup and Configuration Peripheral Scatter-Gather, µDMA Copy Sequence Digital I/O Pads Analog/Digital I/O Pads GPIODATA Write Example	495 496 522 523 583 591 594 595 650 652
Figure 7-2. Figure 7-3. Figure 7-4. Figure 8-1. Figure 8-2. Figure 9-1. Figure 9-2. Figure 9-3. Figure 9-5. Figure 9-6. Figure 10-1. Figure 10-2. Figure 10-3. Figure 10-4.	Using a Crystal as the Hibernation Clock Source with a Single Battery Source Using a Dedicated Oscillator as the Hibernation Clock Source with VDD3ON Mode Using a Regulator for Both V _{DD} and V _{BAT} Internal Memory Block Diagram EEPROM Block Diagram µDMA Block Diagram Example of Ping-Pong µDMA Transaction Memory Scatter-Gather, Setup and Configuration Memory Scatter-Gather, µDMA Copy Sequence Peripheral Scatter-Gather, Setup and Configuration Peripheral Scatter-Gather, µDMA Copy Sequence Digital I/O Pads Analog/Digital I/O Pads GPIODATA Write Example GPIODATA Read Example	495 496 522 583 589 591 592 594 595 650 651 652 705
Figure 7-2. Figure 7-3. Figure 8-1. Figure 8-2. Figure 9-1. Figure 9-2. Figure 9-3. Figure 9-4. Figure 9-5. Figure 9-6. Figure 10-1. Figure 10-2. Figure 10-3. Figure 10-4. Figure 11-1.	Using a Crystal as the Hibernation Clock Source with a Single Battery Source Using a Dedicated Oscillator as the Hibernation Clock Source with VDD3ON Mode Using a Regulator for Both V _{DD} and V _{BAT} Internal Memory Block Diagram EEPROM Block Diagram EXAMPLE OF Ping-Pong µDMA Transaction Memory Scatter-Gather, Setup and Configuration Memory Scatter-Gather, µDMA Copy Sequence Peripheral Scatter-Gather, Setup and Configuration Peripheral Scatter-Gather, µDMA Copy Sequence Digital I/O Pads Analog/Digital I/O Pads GPIODATA Write Example GPIODATA Read Example GPTM Module Block Diagram	495 496 522 583 589 591 592 595 650 651 652 705 712
Figure 7-2. Figure 7-3. Figure 7-4. Figure 8-1. Figure 8-2. Figure 9-1. Figure 9-3. Figure 9-4. Figure 9-5. Figure 9-6. Figure 10-1. Figure 10-2. Figure 10-3. Figure 10-4. Figure 11-1. Figure 11-2.	Using a Crystal as the Hibernation Clock Source with a Single Battery Source Using a Dedicated Oscillator as the Hibernation Clock Source with VDD3ON Mode Using a Regulator for Both VDD and VBAT Internal Memory Block Diagram EEPROM Block Diagram EXAMPLE OF Ping-Pong µDMA Transaction Memory Scatter-Gather, Setup and Configuration Memory Scatter-Gather, µDMA Copy Sequence Peripheral Scatter-Gather, Setup and Configuration Peripheral Scatter-Gather, µDMA Copy Sequence Digital I/O Pads Analog/Digital I/O Pads GPIODATA Write Example GPIODATA Read Example GPTM Module Block Diagram Reading the RTC Value	495 496 522 583 589 591 592 595 650 651 652 712 714
Figure 7-2. Figure 7-3. Figure 7-4. Figure 8-1. Figure 8-2. Figure 9-1. Figure 9-2. Figure 9-3. Figure 9-4. Figure 9-6. Figure 10-1. Figure 10-2. Figure 10-3. Figure 10-4. Figure 11-1. Figure 11-2. Figure 11-3.	Using a Crystal as the Hibernation Clock Source with a Single Battery Source Using a Dedicated Oscillator as the Hibernation Clock Source with VDD3ON Mode Using a Regulator for Both VDD and VBAT Internal Memory Block Diagram EEPROM Block Diagram µDMA Block Diagram Example of Ping-Pong µDMA Transaction Memory Scatter-Gather, Setup and Configuration Memory Scatter-Gather, µDMA Copy Sequence Peripheral Scatter-Gather, Setup and Configuration Peripheral Scatter-Gather, µDMA Copy Sequence Digital I/O Pads Analog/Digital I/O Pads GPIODATA Write Example GPIODATA Read Example GPTM Module Block Diagram Reading the RTC Value Input Edge-Count Mode Example, Counting Down	495 496 522 583 589 591 592 595 650 652 705 712 714
Figure 7-2. Figure 7-3. Figure 7-4. Figure 8-1. Figure 8-2. Figure 9-1. Figure 9-2. Figure 9-3. Figure 9-5. Figure 9-6. Figure 10-1. Figure 10-2. Figure 10-3. Figure 11-1. Figure 11-2. Figure 11-3. Figure 11-3. Figure 11-4.	Using a Crystal as the Hibernation Clock Source with a Single Battery Source Using a Dedicated Oscillator as the Hibernation Clock Source with VDD3ON Mode Using a Regulator for Both V _{DD} and V _{BAT} Internal Memory Block Diagram EEPROM Block Diagram Example of Ping-Pong µDMA Transaction Memory Scatter-Gather, Setup and Configuration Memory Scatter-Gather, µDMA Copy Sequence Peripheral Scatter-Gather, Setup and Configuration Peripheral Scatter-Gather, µDMA Copy Sequence Digital I/O Pads Analog/Digital I/O Pads GPIODATA Write Example GPIODATA Read Example GPTM Module Block Diagram Reading the RTC Value Input Edge-Count Mode Example, Counting Down 16-Bit Input Edge-Time Mode Example	495 496 522 523 583 591 592 594 595 650 652 715 714 715

Figure 11-8.	CCP Output, GPTMTnILR > GPTMTnMATCHR	718
Figure 11-9.	Timer Daisy Chain	719
Figure 12-1.	WDT Module Block Diagram	775
Figure 13-1.	Implementation of Two ADC Blocks	800
Figure 13-2.	ADC Module Block Diagram	801
Figure 13-3.	ADC Sample Phases	805
Figure 13-4.	Doubling the ADC Sample Rate	805
Figure 13-5.	Skewed Sampling	806
Figure 13-6.	Sample Averaging Example	807
Figure 13-7.	ADC Input Equivalency Diagram	808
Figure 13-8.	ADC Voltage Reference	
Figure 13-9.	ADC Conversion Result	810
Figure 13-10.	Differential Voltage Representation	812
	Internal Temperature Sensor Characteristic	
	Low-Band Operation (CIC=0x0 and/or CTC=0x0)	
Figure 13-13.	Mid-Band Operation (CIC=0x1 and/or CTC=0x1)	816
Figure 13-14.	High-Band Operation (CIC=0x3 and/or CTC=0x3)	817
Figure 14-1.	UART Module Block Diagram	
Figure 14-2.	UART Character Frame	
Figure 14-3.	IrDA Data Modulation	903
Figure 15-1.	SSI Module Block Diagram	
Figure 15-2.	TI Synchronous Serial Frame Format (Single Transfer)	
Figure 15-3.	TI Synchronous Serial Frame Format (Continuous Transfer)	
Figure 15-4.	Freescale SPI Format (Single Transfer) with SPO=0 and SPH=0	
Figure 15-5.	Freescale SPI Format (Continuous Transfer) with SPO=0 and SPH=0	
Figure 15-6.	Freescale SPI Frame Format with SPO=0 and SPH=1	
Figure 15-7.	Freescale SPI Frame Format (Single Transfer) with SPO=1 and SPH=0	
Figure 15-8.	Freescale SPI Frame Format (Continuous Transfer) with SPO=1 and SPH=0	
Figure 15-9.	Freescale SPI Frame Format with SPO=1 and SPH=1	
•	MICROWIRE Frame Format (Single Frame)	
-	MICROWIRE Frame Format (Continuous Transfer)	
	MICROWIRE Frame Format, SSIFss Input Setup and Hold Requirements	
Figure 16-1.	I ² C Block Diagram	
Figure 16-2.	I ² C Bus Configuration	1004
Figure 16-3.	START and STOP Conditions	
Figure 16-4.	Complete Data Transfer with a 7-Bit Address	
Figure 16-5.	R/S Bit in First Byte	
Figure 16-6.	Data Validity During Bit Transfer on the I ² C Bus	
Figure 16-7.	High-Speed Data Format	
Figure 16-8.	Master Single TRANSMIT	
Figure 16-9.	Master Single RECEIVE	
•	Master TRANSMIT of Multiple Data Bytes	
-	Master RECEIVE of Multiple Data Bytes	
-	Master RECEIVE with Repeated START after Master TRANSMIT	
•	Master TRANSMIT with Repeated START after Master RECEIVE	
-	High Speed Mode Master Transmit	
	Slave Command Sequence	
-	CAN Controller Block Diagram	

Figure 17-2.	CAN Data/Remote Frame	. 1056
Figure 17-3.	Message Objects in a FIFO Buffer	. 1064
Figure 17-4.	CAN Bit Time	. 1068
Figure 18-1.	USB Module Block Diagram	. 1105
Figure 19-1.	Analog Comparator Module Block Diagram	. 1220
Figure 19-2.	Structure of Comparator Unit	
Figure 19-3.	Comparator Internal Reference Structure	. 1222
Figure 20-1.	PWM Module Diagram	
Figure 20-2.	PWM Generator Block Diagram	. 1237
Figure 20-3.	PWM Count-Down Mode	. 1240
Figure 20-4.	PWM Count-Up/Down Mode	. 1241
Figure 20-5.	PWM Generation Example In Count-Up/Down Mode	. 1241
Figure 20-6.	PWM Dead-Band Generator	
Figure 21-1.	QEI Block Diagram	. 1314
Figure 21-2.	Quadrature Encoder and Velocity Predivider Operation	. 1316
Figure 22-1.	100-Pin LQFP Package Pin Diagram	. 1335
Figure 24-1.	Load Conditions	
Figure 24-2.	JTAG Test Clock Input Timing	
Figure 24-3.	JTAG Test Access Port (TAP) Timing	. 1382
Figure 24-4.	Power Assertions versus VDDA Levels	
Figure 24-5.	Power and Brown-Out Assertions versus VDD Levels	. 1385
Figure 24-6.	POK assertion vs VDDC	. 1386
Figure 24-7.	POR-BOR0-BOR1 VDD Glitch Response	. 1386
Figure 24-8.	POR-BOR0-BOR1 VDD Droop Response	
Figure 24-9.	Digital Power-On Reset Timing	
Figure 24-10.	Brown-Out Reset Timing	
	External Reset Timing (RST)	
	Software Reset Timing	
-	Watchdog Reset Timing	
-	MOSC Failure Reset Timing	
-	Hibernation Module Timing	
-	ESD Protection on Fail-Safe Pins	
-	ESD Protection on Non-Fail-Safe Pins	
-	ADC External Reference Filtering	
-	ADC Input Equivalency Diagram	
-	SSI Timing for TI Frame Format (FRF=01), Single Transfer Timing	
5	Measurement	1407
Figure 24-21.	SSI Timing for MICROWIRE Frame Format (FRF=10), Single Transfer	. 1408
-	SSI Timing for SPI Frame Format (FRF=00), with SPH=1	
•	I ² C Timing	
	Stellaris® LM4F232H5QC 100-Pin LQFP Package Dimensions	

List of Tables

Table 1.	Revision History	
Table 2.	Documentation Conventions	47
Table 1-1.	Stellaris LM4F Device Series	50
Table 1-2.	LM4F232H5QC Microcontroller Features	51
Table 2-1.	Summary of Processor Mode, Privilege Level, and Stack Use	78
Table 2-2.	Processor Register Map	79
Table 2-3.	PSR Register Combinations	85
Table 2-4.	Memory Map	96
Table 2-5.	Memory Access Behavior	100
Table 2-6.	SRAM Memory Bit-Banding Regions	102
Table 2-7.	Peripheral Memory Bit-Banding Regions	102
Table 2-8.	Exception Types	107
Table 2-9.	Interrupts	108
Table 2-10.	Exception Return Behavior	115
Table 2-11.	Faults	116
Table 2-12.	Fault Status and Fault Address Registers	117
Table 2-13.	Cortex-M4F Instruction Summary	119
Table 3-1.	Core Peripheral Register Regions	126
Table 3-2.	Memory Attributes Summary	130
Table 3-3.	TEX, S, C, and B Bit Field Encoding	132
Table 3-4.	Cache Policy for Memory Attribute Encoding	133
Table 3-5.	AP Bit Field Encoding	133
Table 3-6.	Memory Region Attributes for Stellaris Microcontrollers	134
Table 3-7.	QNaN and SNaN Handling	137
Table 3-8.	Peripherals Register Map	138
Table 3-9.	Interrupt Priority Levels	168
Table 3-10.	Example SIZE Field Values	196
Table 4-1.	JTAG_SWD_SWO Signals (100LQFP)	205
Table 4-2.	JTAG Port Pins State after Power-On Reset or RST assertion	206
Table 4-3.	JTAG Instruction Register Commands	212
Table 5-1.	System Control & Clocks Signals (100LQFP)	216
Table 5-2.	Reset Sources	217
Table 5-3.	Clock Source Options	224
Table 5-4.	Possible System Clock Frequencies Using the SYSDIV Field	227
Table 5-5.	Examples of Possible System Clock Frequencies Using the SYSDIV2 Field	227
Table 5-6.	Examples of Possible System Clock Frequencies with DIV400=1	228
Table 5-7.	System Control Register Map	234
Table 5-8.	RCC2 Fields that Override RCC Fields	263
Table 6-1.	System Exception Register Map	483
Table 7-1.	Hibernate Signals (100LQFP)	
Table 7-2.	Counter Behavior with a TRIM Value of 0x8003	498
Table 7-3.	Counter Behavior with a TRIM Value of 0x7FFC	499
Table 7-4.	Hibernation Module Clock Operation	502
Table 7-5.	Hibernation Module Register Map	503
Table 8-1.	Flash Memory Protection Policy Combinations	527
Table 8-2.	User-Programmable Flash Memory Resident Registers	531

Table 8-3.	Flash Register Map	537
Table 9-1.	μDMA Channel Assignments	584
Table 9-2.	Request Type Support	586
Table 9-3.	Control Structure Memory Map	587
Table 9-4.	Channel Control Structure	587
Table 9-5.	μDMA Read Example: 8-Bit Peripheral	596
Table 9-6.	μDMA Interrupt Assignments	597
Table 9-7.	Channel Control Structure Offsets for Channel 30	598
Table 9-8.	Channel Control Word Configuration for Memory Transfer Example	598
Table 9-9.	Channel Control Structure Offsets for Channel 7	599
Table 9-10.	Channel Control Word Configuration for Peripheral Transmit Example	600
Table 9-11.	Primary and Alternate Channel Control Structure Offsets for Channel 8	
Table 9-12.	Channel Control Word Configuration for Peripheral Ping-Pong Receive Example	602
Table 9-13.	μDMA Register Map	
Table 10-1.	GPIO Pins With Non-Zero Reset Values	
Table 10-2.	GPIO Pins and Alternate Functions (100LQFP)	647
Table 10-3.	GPIO Pad Configuration Examples	
Table 10-4.	GPIO Interrupt Configuration Example	
Table 10-5.	GPIO Pins With Non-Zero Reset Values	
Table 10-6.	GPIO Register Map	
Table 10-7.	GPIO Pins With Non-Zero Reset Values	
Table 10-8.	GPIO Pins With Non-Zero Reset Values	676
Table 10-9.	GPIO Pins With Non-Zero Reset Values	678
Table 10-10.	GPIO Pins With Non-Zero Reset Values	681
Table 10-11.	GPIO Pins With Non-Zero Reset Values	688
Table 11-1.	Available CCP Pins	706
Table 11-2.	General-Purpose Timers Signals (100LQFP)	706
Table 11-3.	General-Purpose Timer Capabilities	708
Table 11-4.	Counter Values When the Timer is Enabled in Periodic or One-Shot Modes	709
Table 11-5.	16-Bit Timer With Prescaler Configurations	711
Table 11-6.	32-Bit Timer (configured in 32/64-bit mode) With Prescaler Configurations	711
Table 11-7.	Counter Values When the Timer is Enabled in RTC Mode	711
Table 11-8.	Counter Values When the Timer is Enabled in Input Edge-Count Mode	713
Table 11-9.	Counter Values When the Timer is Enabled in Input Event-Count Mode	714
Table 11-10.	Counter Values When the Timer is Enabled in PWM Mode	716
Table 11-11.	Timeout Actions for GPTM Modes	719
Table 11-12.	Timers Register Map	726
Table 12-1.	Watchdog Timers Register Map	777
Table 13-1.	ADC Signals (100LQFP)	801
Table 13-2.	Samples and FIFO Depth of Sequencers	803
Table 13-3.	Differential Sampling Pairs	810
Table 13-4.	ADC Register Map	818
Table 14-1.	UART Signals (100LQFP)	899
Table 14-2.	Flow Control Mode	905
Table 14-3.	UART Register Map	909
Table 15-1.	SSI Signals (100LQFP)	960
Table 15-2.	SSI Register Map	972

Table 16-1.	I2C Signals (100LQFP)	1003
Table 16-2.	Examples of I ² C Master Timer Period versus Speed Mode	1009
Table 16-3.	Examples of I ² C Master Timer Period in High-Speed Mode	1010
Table 16-4.	Inter-Integrated Circuit (I ² C) Interface Register Map	1022
Table 16-5.	Write Field Decoding for I2CMCS[3:0] Field	1028
Table 17-1.	Controller Area Network Signals (100LQFP)	1055
Table 17-2.	Message Object Configurations	1061
Table 17-3.	CAN Protocol Ranges	1068
Table 17-4.	CANBIT Register Values	1068
Table 17-5.	CAN Register Map	1072
Table 18-1.	USB Signals (100LQFP)	1106
Table 18-2.	Remainder (MAXLOAD/4)	1117
Table 18-3.	Actual Bytes Read	1117
Table 18-4.	Packet Sizes That Clear RXRDY	1118
Table 18-5.	Universal Serial Bus (USB) Controller Register Map	1119
Table 19-1.	Analog Comparators Signals (100LQFP)	1220
Table 19-2.	Internal Reference Voltage and ACREFCTL Field Values	1222
Table 19-3.	Analog Comparator Voltage Reference Characteristics, V _{DDA} = 3.3V, EN= 1, and RNG = 0	1223
Table 19-4.	Analog Comparator Voltage Reference Characteristics, V _{DDA} = 3.3V, EN= 1, and RNG = 1	1224
Table 19-5.	Analog Comparators Register Map	1225
Table 20-1.	PWM Signals (100LQFP)	
Table 20-2.	PWM Register Map	1246
Table 21-1.	QEI Signals (100LQFP)	1314
Table 21-2.	QEI Register Map	1318
Table 23-1.	GPIO Pins With Default Alternate Functions	1336
Table 23-2.	Signals by Pin Number	1337
Table 23-3.	Signals by Signal Name	1348
Table 23-4.	Signals by Function, Except for GPIO	1358
Table 23-5.	GPIO Pins and Alternate Functions	
Table 23-6.	Possible Pin Assignments for Alternate Functions	1370
Table 23-7.	Connections for Unused Signals (100-Pin LQFP)	1375
Table 24-1.	Temperature Characteristics	1376
Table 24-2.	Thermal Characteristics	1376
Table 24-3.	ESD Absolute Maximum Ratings	1376
Table 24-4.	Maximum Ratings	1377
Table 24-5.	Recommended DC Operating Conditions	
Table 24-6.	Recommended GPIO Pad Operating Conditions	1378
Table 24-7.	GPIO Current Restrictions	
Table 24-8.	GPIO Package Side Assignments	1379
Table 24-9.	JTAG Characteristics	
Table 24-10.	Power-On and Brown-Out Levels	
Table 24-11.	Reset Characteristics	
Table 24-12.	LDO Regulator Characteristics	
Table 24-13.	Phase Locked Loop (PLL) Characteristics	
Table 24-14.	Actual PLL Frequency	1391
Table 24-15	PIOSC Clock Characteristics	1392

Table 24-16.	Low-Frequency internal Oscillator Characteristics	1392
Table 24-17.	Hibernation Oscillator Input Characteristics	1392
Table 24-18.	Main Oscillator Input Characteristics	1393
Table 24-19.	Crystal Parameters	1394
Table 24-20.	Supported MOSC Crystal Frequencies	1395
Table 24-21.	System Clock Characteristics with ADC Operation	1396
Table 24-22.	System Clock Characteristics with USB Operation	1396
Table 24-23.	Sleep Modes AC Characteristics	1397
Table 24-24.	Hibernation Module Battery Characteristics	1398
Table 24-25.	Hibernation Module AC Characteristics	1398
Table 24-26.	Flash Memory Characteristics	1399
Table 24-27.	EEPROM Characteristics	1399
Table 24-28.	GPIO Module Characteristics	1400
Table 24-29.	Pad Voltage/Current Characteristics for Fail-Safe Pins	1401
Table 24-30.	Non-Fail-Safe I/O Pad Voltage/Current Characteristics	1402
Table 24-31.	ADC Electrical Characteristics	1403
Table 24-32.	SSI Characteristics	1407
Table 24-33.	I ² C Characteristics	1409
Table 24-34.	Analog Comparator Characteristics	1411
Table 24-35.	Analog Comparator Voltage Reference Characteristics	1411
Table 24-36.	Analog Comparator Voltage Reference Characteristics, V _{DDA} = 3.3V, EN= 1, and	
	RNG = 0	1411
Table 24-37.	Analog Comparator Voltage Reference Characteristics, V _{DDA} = 3.3V, EN= 1, and	
	RNG = 1	1412
Table 24-38.	Preliminary Current Consumption	1413
Table A-1.	Part Ordering Information	1415

List of Registers

The Cortex	-M4F Processor	73
Register 1:	Cortex General-Purpose Register 0 (R0)	81
Register 2:	Cortex General-Purpose Register 1 (R1)	81
Register 3:	Cortex General-Purpose Register 2 (R2)	81
Register 4:	Cortex General-Purpose Register 3 (R3)	81
Register 5:	Cortex General-Purpose Register 4 (R4)	81
Register 6:	Cortex General-Purpose Register 5 (R5)	
Register 7:	Cortex General-Purpose Register 6 (R6)	81
Register 8:	Cortex General-Purpose Register 7 (R7)	81
Register 9:	Cortex General-Purpose Register 8 (R8)	81
Register 10:	Cortex General-Purpose Register 9 (R9)	
Register 11:	Cortex General-Purpose Register 10 (R10)	
Register 12:	Cortex General-Purpose Register 11 (R11)	
Register 13:	Cortex General-Purpose Register 12 (R12)	81
Register 14:	Stack Pointer (SP)	
Register 15:	Link Register (LR)	
Register 16:	Program Counter (PC)	
Register 17:	Program Status Register (PSR)	
Register 18:	Priority Mask Register (PRIMASK)	
Register 19:	Fault Mask Register (FAULTMASK)	
Register 20:	Base Priority Mask Register (BASEPRI)	
Register 21:	Control Register (CONTROL)	
Register 22:	Floating-Point Status Control (FPSC)	94
Cortex-M4	Peripherals	
Register 1:	SysTick Control and Status Register (STCTRL), offset 0x010	
Register 2:	SysTick Reload Value Register (STRELOAD), offset 0x014	
Register 3:	SysTick Current Value Register (STCURRENT), offset 0x018	145
Register 4:	Interrupt 0-31 Set Enable (EN0), offset 0x100	
Register 5:	Interrupt 32-63 Set Enable (EN1), offset 0x104	
Register 6:	Interrupt 64-95 Set Enable (EN2), offset 0x108	
Register 7:	Interrupt 96-127 Set Enable (EN3), offset 0x10C	
Register 8:	Interrupt 128-138 Set Enable (EN4), offset 0x110	
Register 9:	Interrupt 0-31 Clear Enable (DIS0), offset 0x180	
Register 10:	Interrupt 32-63 Clear Enable (DIS1), offset 0x184	
Register 11:	Interrupt 64-95 Clear Enable (DIS2), offset 0x188	
Register 12:	Interrupt 96-127 Clear Enable (DIS3), offset 0x18C	
Register 13:	Interrupt 128-138 Clear Enable (DIS4), offset 0x190	
Register 14:	Interrupt 0-31 Set Pending (PEND0), offset 0x200	
Register 15:	Interrupt 32-63 Set Pending (PEND1), offset 0x204	
Register 16:	Interrupt 64-95 Set Pending (PEND2), offset 0x208	
Register 17:	Interrupt 96-127 Set Pending (PEND3), offset 0x20C	
Register 18:	Interrupt 128-138 Set Pending (PEND4), offset 0x210	
Register 19:	Interrupt 0-31 Clear Pending (UNPENDO), offset 0x280	
Register 20:	Interrupt 32-63 Clear Pending (UNPEND1), offset 0x284	152
Register 21:	Interrupt 64-95 Clear Pending (UNPEND2), offset 0x288	

Register 22:	Interrupt 96-127 Clear Pending (UNPEND3), offset 0x28C	152
Register 23:	Interrupt 128-138 Clear Pending (UNPEND4), offset 0x290	153
Register 24:	Interrupt 0-31 Active Bit (ACTIVE0), offset 0x300	154
Register 25:	Interrupt 32-63 Active Bit (ACTIVE1), offset 0x304	154
Register 26:	Interrupt 64-95 Active Bit (ACTIVE2), offset 0x308	154
Register 27:	Interrupt 96-127 Active Bit (ACTIVE3), offset 0x30C	154
Register 28:	Interrupt 128-138 Active Bit (ACTIVE4), offset 0x310	155
Register 29:	Interrupt 0-3 Priority (PRI0), offset 0x400	156
Register 30:	Interrupt 4-7 Priority (PRI1), offset 0x404	156
Register 31:	Interrupt 8-11 Priority (PRI2), offset 0x408	156
Register 32:	Interrupt 12-15 Priority (PRI3), offset 0x40C	156
Register 33:	Interrupt 16-19 Priority (PRI4), offset 0x410	156
Register 34:	Interrupt 20-23 Priority (PRI5), offset 0x414	156
Register 35:	Interrupt 24-27 Priority (PRI6), offset 0x418	156
Register 36:	Interrupt 28-31 Priority (PRI7), offset 0x41C	156
Register 37:	Interrupt 32-35 Priority (PRI8), offset 0x420	156
Register 38:	Interrupt 36-39 Priority (PRI9), offset 0x424	156
Register 39:	Interrupt 40-43 Priority (PRI10), offset 0x428	
Register 40:	Interrupt 44-47 Priority (PRI11), offset 0x42C	
Register 41:	Interrupt 48-51 Priority (PRI12), offset 0x430	
Register 42:	Interrupt 52-55 Priority (PRI13), offset 0x434	
Register 43:	Interrupt 56-59 Priority (PRI14), offset 0x438	
Register 44:	Interrupt 60-63 Priority (PRI15), offset 0x43C	
Register 45:	Interrupt 64-67 Priority (PRI16), offset 0x440	
Register 46:	Interrupt 68-71 Priority (PRI17), offset 0x444	
Register 47:	Interrupt 72-75 Priority (PRI18), offset 0x448	
Register 48:	Interrupt 76-79 Priority (PRI19), offset 0x44C	
Register 49:	Interrupt 80-83 Priority (PRI20), offset 0x450	
Register 50:	Interrupt 84-87 Priority (PRI21), offset 0x454	
Register 51:	Interrupt 88-91 Priority (PRI22), offset 0x458	
Register 52:	Interrupt 92-95 Priority (PRI23), offset 0x45C	
Register 53:	Interrupt 96-99 Priority (PRI24), offset 0x460	158
Register 54:	Interrupt 100-103 Priority (PRI25), offset 0x464	
Register 55:	Interrupt 104-107 Priority (PRI26), offset 0x468	158
Register 56:	Interrupt 108-111 Priority (PRI27), offset 0x46C	
Register 57:	Interrupt 112-115 Priority (PRI28), offset 0x470	158
Register 58:	Interrupt 116-119 Priority (PRI29), offset 0x474	
Register 59:	Interrupt 120-123 Priority (PRI30), offset 0x478	158
Register 60:	Interrupt 124-127 Priority (PRI31), offset 0x47C	
Register 61:	Interrupt 128-131 Priority (PRI32), offset 0x480	
Register 62:	Interrupt 132-135 Priority (PRI33), offset 0x484	
Register 63:	Interrupt 136-138 Priority (PRI34), offset 0x488	
Register 64:	Software Trigger Interrupt (SWTRIG), offset 0xF00	
Register 65:	Auxiliary Control (ACTLR), offset 0x008	
Register 66:	CPU ID Base (CPUID), offset 0xD00	
Register 67:	Interrupt Control and State (INTCTRL), offset 0xD04	
Register 68:	Vector Table Offset (VTABLE), offset 0xD08	
Register 69:	Application Interrupt and Reset Control (APINT), offset 0xD0C	

Register 70:	System Control (SYSCTRL), offset 0xD10	170
Register 71:	Configuration and Control (CFGCTRL), offset 0xD14	172
Register 72:	System Handler Priority 1 (SYSPRI1), offset 0xD18	174
Register 73:	System Handler Priority 2 (SYSPRI2), offset 0xD1C	175
Register 74:	System Handler Priority 3 (SYSPRI3), offset 0xD20	176
Register 75:	System Handler Control and State (SYSHNDCTRL), offset 0xD24	177
Register 76:	Configurable Fault Status (FAULTSTAT), offset 0xD28	
Register 77:	Hard Fault Status (HFAULTSTAT), offset 0xD2C	187
Register 78:	Memory Management Fault Address (MMADDR), offset 0xD34	188
Register 79:	Bus Fault Address (FAULTADDR), offset 0xD38	189
Register 80:	MPU Type (MPUTYPE), offset 0xD90	190
Register 81:	MPU Control (MPUCTRL), offset 0xD94	191
Register 82:	MPU Region Number (MPUNUMBER), offset 0xD98	193
Register 83:	MPU Region Base Address (MPUBASE), offset 0xD9C	
Register 84:	MPU Region Base Address Alias 1 (MPUBASE1), offset 0xDA4	
Register 85:	MPU Region Base Address Alias 2 (MPUBASE2), offset 0xDAC	
Register 86:	MPU Region Base Address Alias 3 (MPUBASE3), offset 0xDB4	
Register 87:	MPU Region Attribute and Size (MPUATTR), offset 0xDA0	
Register 88:	MPU Region Attribute and Size Alias 1 (MPUATTR1), offset 0xDA8	
Register 89:	MPU Region Attribute and Size Alias 2 (MPUATTR2), offset 0xDB0	
Register 90:	MPU Region Attribute and Size Alias 3 (MPUATTR3), offset 0xDB8	
Register 91:	Coprocessor Access Control (CPAC), offset 0xD88	
Register 92:	Floating-Point Context Control (FPCC), offset 0xF34	
Register 93:	Floating-Point Context Address (FPCA), offset 0xF38	
Register 94:	Floating-Point Default Status Control (FPDSC), offset 0xF3C	
•	ntrol	
Register 1:	Device Identification 0 (DID0), offset 0x000	
Register 2:	Device Identification 1 (DID1), offset 0x004	
Register 3:	Brown-Out Reset Control (PBORCTL), offset 0x030	
Register 4:	Raw Interrupt Status (RIS), offset 0x050	
Register 5:	Interrupt Mask Control (IMC), offset 0x054	
Register 6:	Masked Interrupt Status and Clear (MISC), offset 0x058	
Register 7:	Reset Cause (RESC), offset 0x05C	
Register 8:	Run-Mode Clock Configuration (RCC), offset 0x060	
Register 9:	GPIO High-Performance Bus Control (GPIOHBCTL), offset 0x06C	
Register 10:	Run-Mode Clock Configuration 2 (RCC2), offset 0x070	
Register 11:	Main Oscillator Control (MOSCCTL), offset 0x07C	
Register 12:	Deep Sleep Clock Configuration (DSLPCLKCFG), offset 0x144	
Register 13:	System Properties (SYSPROP), offset 0x14C	
Register 14:	Precision Internal Oscillator Calibration (PIOSCCAL), offset 0x150	
Register 15:	Precision Internal Oscillator Statistics (PIOSCSTAT), offset 0x154	
Register 16:	PLL Frequency 0 (PLLFREQ0), offset 0x160	
Register 17:	PLL Frequency 1 (PLLFREQ1), offset 0x164	
Register 18:	PLL Status (PLLSTAT), offset 0x168	
Register 19:	Watchdog Timer Peripheral Present (PPWD), offset 0x300	
Register 20:	16/32-Bit General-Purpose Timer Peripheral Present (PPTIMER), offset 0x304	
Register 21:	General-Purpose Input/Output Peripheral Present (PPGPIO), offset 0x308	
Register 21.	Micro Direct Memory Access Peripheral Present (PPDMA) offset 0x300	282
REUISIER 11.		/ / /

Register 23:	Hibernation Peripheral Present (PPHIB), offset 0x314	283
Register 24:	Universal Asynchronous Receiver/Transmitter Peripheral Present (PPUART), offset 0x318	284
Register 25:	Synchronous Serial Interface Peripheral Present (PPSSI), offset 0x31C	286
Register 26:	Inter-Integrated Circuit Peripheral Present (PPI2C), offset 0x320	
Register 27:	Universal Serial Bus Peripheral Present (PPUSB), offset 0x328	
Register 28:	Controller Area Network Peripheral Present (PPCAN), offset 0x334	
Register 29:	Analog-to-Digital Converter Peripheral Present (PPADC), offset 0x338	
Register 30:	Analog Comparator Peripheral Present (PPACMP), offset 0x33C	
Register 31:	Pulse Width Modulator Peripheral Present (PPPWM), offset 0x340	
Register 32:	Quadrature Encoder Interface Peripheral Present (PPQEI), offset 0x344	
Register 33:	EEPROM Peripheral Present (PPEEPROM), offset 0x358	
Register 34:	32/64-Bit Wide General-Purpose Timer Peripheral Present (PPWTIMER), offset 0x35C	
Register 35:	Watchdog Timer Software Reset (SRWD), offset 0x500	
Register 36:	16/32-Bit General-Purpose Timer Software Reset (SRTIMER), offset 0x504	
Register 37:	General-Purpose Input/Output Software Reset (SRGPIO), offset 0x508	
Register 38:	Micro Direct Memory Access Software Reset (SRDMA), offset 0x50C	
Register 39:	Hibernation Software Reset (SRHIB), offset 0x514	
Register 40:	Universal Asynchronous Receiver/Transmitter Software Reset (SRUART), offset 0x518	
Register 41:	Synchronous Serial Interface Software Reset (SRSSI), offset 0x51C	
Register 42:	Inter-Integrated Circuit Software Reset (SRI2C), offset 0x520	
Register 43:	Universal Serial Bus Software Reset (SRUSB), offset 0x528	
Register 44:	Controller Area Network Software Reset (SRCAN), offset 0x534	
Register 45:	Analog-to-Digital Converter Software Reset (SRADC), offset 0x538	
Register 46:	Analog Comparator Software Reset (SRACMP), offset 0x53C	
Register 47:	Pulse Width Modulator Software Reset (SRPWM), offset 0x540	
Register 48:	Quadrature Encoder Interface Software Reset (SRQEI), offset 0x544	
Register 49:	EEPROM Software Reset (SREEPROM), offset 0x558	
Register 50:	32/64-Bit Wide General-Purpose Timer Software Reset (SRWTIMER), offset 0x55C	
•		
Register 51:	Watchdog Timer Run Mode Clock Gating Control (RCGCWD), offset 0x600	. 321
Register 52:	16/32-Bit General-Purpose Timer Run Mode Clock Gating Control (RCGCTIMER), offset 0x604	328
Register 53:	General-Purpose Input/Output Run Mode Clock Gating Control (RCGCGPIO), offset 0x608	330
Register 54:	Micro Direct Memory Access Run Mode Clock Gating Control (RCGCDMA), offset	
	0x60C	
Register 55:	Hibernation Run Mode Clock Gating Control (RCGCHIB), offset 0x614	. 334
Register 56:	Universal Asynchronous Receiver/Transmitter Run Mode Clock Gating Control (RCGCUART), offset 0x618	335
Register 57:	Synchronous Serial Interface Run Mode Clock Gating Control (RCGCSSI), offset 0x61C	337
Register 58:	Inter-Integrated Circuit Run Mode Clock Gating Control (RCGCI2C), offset 0x620	339
Register 59:	Universal Serial Bus Run Mode Clock Gating Control (RCGCUSB), offset 0x628	
Register 60:	Controller Area Network Run Mode Clock Gating Control (RCGCCAN), offset 0x634	
Register 61:	Analog-to-Digital Converter Run Mode Clock Gating Control (RCGCADC), offset 0x638	
Register 62:	Analog Comparator Run Mode Clock Gating Control (RCGCACMP), offset 0x63C	
Register 63:	Pulse Width Modulator Run Mode Clock Gating Control (RCGCPWM), offset 0x640	
Register 64:	Quadrature Encoder Interface Run Mode Clock Gating Control (RCGCQEI), offset	
J	0x644	346

Register 65:	EEPROM Run Mode Clock Gating Control (RCGCEEPROM), offset 0x658	. 347
Register 66:	32/64-Bit Wide General-Purpose Timer Run Mode Clock Gating Control (RCGCWTIMER), offset 0x65C	348
Register 67:	Watchdog Timer Sleep Mode Clock Gating Control (SCGCWD), offset 0x700	350
Register 68:	16/32-Bit General-Purpose Timer Sleep Mode Clock Gating Control (SCGCTIMER), offset 0x704	351
Register 69:	General-Purpose Input/Output Sleep Mode Clock Gating Control (SCGCGPIO), offset 0x708	353
Register 70:	Micro Direct Memory Access Sleep Mode Clock Gating Control (SCGCDMA), offset 0x70C	356
Register 71:	Hibernation Sleep Mode Clock Gating Control (SCGCHIB), offset 0x714	357
Register 72:	Universal Asynchronous Receiver/Transmitter Sleep Mode Clock Gating Control (SCGCUART), offset 0x718	358
Register 73:	Synchronous Serial Interface Sleep Mode Clock Gating Control (SCGCSSI), offset 0x71C	360
Register 74:	Inter-Integrated Circuit Sleep Mode Clock Gating Control (SCGCI2C), offset 0x720	362
Register 75:	Universal Serial Bus Sleep Mode Clock Gating Control (SCGCUSB), offset 0x728	364
Register 76:	Controller Area Network Sleep Mode Clock Gating Control (SCGCCAN), offset 0x734	. 365
Register 77:	Analog-to-Digital Converter Sleep Mode Clock Gating Control (SCGCADC), offset 0x738	366
Register 78:	Analog Comparator Sleep Mode Clock Gating Control (SCGCACMP), offset 0x73C	
Register 79:	Pulse Width Modulator Sleep Mode Clock Gating Control (SCGCPWM), offset 0x740	368
Register 80:	Quadrature Encoder Interface Sleep Mode Clock Gating Control (SCGCQEI), offset 0x744	369
Register 81:	EEPROM Sleep Mode Clock Gating Control (SCGCEEPROM), offset 0x758	
Register 82:	32/64-Bit Wide General-Purpose Timer Sleep Mode Clock Gating Control (SCGCWTIMER), offset 0x75C	371
Register 83:	Watchdog Timer Deep-Sleep Mode Clock Gating Control (DCGCWD), offset 0x800	-
Register 84:	16/32-Bit General-Purpose Timer Deep-Sleep Mode Clock Gating Control (DCGCTIMER), offset 0x804	374
Register 85:	General-Purpose Input/Output Deep-Sleep Mode Clock Gating Control (DCGCGPIO), offset 0x808	376
Register 86:	Micro Direct Memory Access Deep-Sleep Mode Clock Gating Control (DCGCDMA), offset 0x80C	379
Register 87:	Hibernation Deep-Sleep Mode Clock Gating Control (DCGCHIB), offset 0x814	380
Register 88:	Universal Asynchronous Receiver/Transmitter Deep-Sleep Mode Clock Gating Control (DCGCUART), offset 0x818	
Register 89:	Synchronous Serial Interface Deep-Sleep Mode Clock Gating Control (DCGCSSI), offset 0x81C	
Register 90:	Inter-Integrated Circuit Deep-Sleep Mode Clock Gating Control (DCGCI2C), offset 0x820	
Register 91:	Universal Serial Bus Deep-Sleep Mode Clock Gating Control (DCGCUSB), offset 0x828	
Register 92:	Controller Area Network Deep-Sleep Mode Clock Gating Control (DCGCCAN), offset 0x834	
Register 93:	Analog-to-Digital Converter Deep-Sleep Mode Clock Gating Control (DCGCADC), offset 0x838	
Register 94:	Analog Comparator Deep-Sleep Mode Clock Gating Control (DCGCACMP), offset 0x83C	

Register 95:	Pulse Width Modulator Deep-Sleep Mode Clock Gating Control (DCGCPWM), offset 0x840	391
Register 96:	Quadrature Encoder Interface Deep-Sleep Mode Clock Gating Control (DCGCQEI), offset 0x844	392
Register 97:	EEPROM Deep-Sleep Mode Clock Gating Control (DCGCEEPROM), offset 0x858	
Register 98:	32/64-Bit Wide General-Purpose Timer Deep-Sleep Mode Clock Gating Control	
	(DCGCWTIMER), offset 0x85C	
Register 99:	Watchdog Timer Peripheral Ready (PRWD), offset 0xA00	
	16/32-Bit General-Purpose Timer Peripheral Ready (PRTIMER), offset 0xA04	
-	General-Purpose Input/Output Peripheral Ready (PRGPIO), offset 0xA08	
•	Micro Direct Memory Access Peripheral Ready (PRDMA), offset 0xA0C	
-	Hibernation Peripheral Ready (PRHIB), offset 0xA14	402
Register 104:	Universal Asynchronous Receiver/Transmitter Peripheral Ready (PRUART), offset 0xA18	403
Register 105:	Synchronous Serial Interface Peripheral Ready (PRSSI), offset 0xA1C	. 405
Register 106:	Inter-Integrated Circuit Peripheral Ready (PRI2C), offset 0xA20	407
Register 107:	Universal Serial Bus Peripheral Ready (PRUSB), offset 0xA28	. 409
Register 108:	Controller Area Network Peripheral Ready (PRCAN), offset 0xA34	. 410
Register 109:	Analog-to-Digital Converter Peripheral Ready (PRADC), offset 0xA38	. 411
•	Analog Comparator Peripheral Ready (PRACMP), offset 0xA3C	
Register 111:	Pulse Width Modulator Peripheral Ready (PRPWM), offset 0xA40	. 413
Register 112:	Quadrature Encoder Interface Peripheral Ready (PRQEI), offset 0xA44	. 414
-	EEPROM Peripheral Ready (PREEPROM), offset 0xA58	
-	32/64-Bit Wide General-Purpose Timer Peripheral Ready (PRWTIMER), offset 0xA5C	
•	Device Capabilities 0 (DC0), offset 0x008	
-	Device Capabilities 1 (DC1), offset 0x010	
-	Device Capabilities 2 (DC2), offset 0x014	
-	Device Capabilities 3 (DC3), offset 0x018	
-	Device Capabilities 4 (DC4), offset 0x01C	
•	Device Capabilities 5 (DC5), offset 0x020	
-	Device Capabilities 6 (DC6), offset 0x024	
-	Device Capabilities 7 (DC7), offset 0x028	
•	Device Capabilities 8 (DC8), offset 0x02C	
•	Software Reset Control 0 (SRCR0), offset 0x040	
-	Software Reset Control 1 (SRCR1), offset 0x044	
-	Software Reset Control 2 (SRCR2), offset 0x048	
	Run Mode Clock Gating Control Register 0 (RCGC0), offset 0x100	
•	Run Mode Clock Gating Control Register 1 (RCGC1), offset 0x104	
•	Run Mode Clock Gating Control Register 2 (RCGC2), offset 0x108	
•	Sleep Mode Clock Gating Control Register 0 (SCGC0), offset 0x110	
•	Sleep Mode Clock Gating Control Register 1 (SCGC1), offset 0x114	
-	Sleep Mode Clock Gating Control Register 2 (SCGC2), offset 0x118	
	Deep Sleep Mode Clock Gating Control Register 0 (DCGC0), offset 0x120	
-	Deep-Sleep Mode Clock Gating Control Register 1 (DCGC1), offset 0x124	
-	Deep Sleep Mode Clock Gating Control Register 2 (DCGC2), offset 0x128	
	Device Capabilities 9 (DC9), offset 0x190	
Register 137	Non-Volatile Memory Information (NVMSTAT) offset 0v1A0	482

System Ex	ception Module	483
Register 1:	System Exception Raw Interrupt Status (SYSEXCRIS), offset 0x000	484
Register 2:	System Exception Interrupt Mask (SYSEXCIM), offset 0x004	486
Register 3:	System Exception Masked Interrupt Status (SYSEXCMIS), offset 0x008	488
Register 4:	System Exception Interrupt Clear (SYSEXCIC), offset 0x00C	490
Hibernation	n Module	491
Register 1:	Hibernation RTC Counter (HIBRTCC), offset 0x000	
Register 2:	Hibernation RTC Match 0 (HIBRTCM0), offset 0x004	
Register 3:	Hibernation RTC Load (HIBRTCLD), offset 0x00C	
Register 4:	Hibernation Control (HIBCTL), offset 0x010	508
Register 5:	Hibernation Interrupt Mask (HIBIM), offset 0x014	512
Register 6:	Hibernation Raw Interrupt Status (HIBRIS), offset 0x018	
Register 7:	Hibernation Masked Interrupt Status (HIBMIS), offset 0x01C	
Register 8:	Hibernation Interrupt Clear (HIBIC), offset 0x020	
Register 9:	Hibernation RTC Trim (HIBRTCT), offset 0x024	519
Register 10:	Hibernation RTC Sub Seconds (HIBRTCSS), offset 0x028	520
Register 11:	Hibernation Data (HIBDATA), offset 0x030-0x06F	521
Internal Me	mory	522
Register 1:	Flash Memory Address (FMA), offset 0x000	
Register 2:	Flash Memory Data (FMD), offset 0x004	
Register 3:	Flash Memory Control (FMC), offset 0x008	
Register 4:	Flash Controller Raw Interrupt Status (FCRIS), offset 0x00C	543
Register 5:	Flash Controller Interrupt Mask (FCIM), offset 0x010	
Register 6:	Flash Controller Masked Interrupt Status and Clear (FCMISC), offset 0x014	548
Register 7:	Flash Memory Control 2 (FMC2), offset 0x020	551
Register 8:	Flash Write Buffer Valid (FWBVAL), offset 0x030	552
Register 9:	Flash Write Buffer n (FWBn), offset 0x100 - 0x17C	553
Register 10:	Flash Size (FSIZE), offset 0xFC0	554
Register 11:	SRAM Size (SSIZE), offset 0xFC4	555
Register 12:	ROM Software Map (ROMSWMAP), offset 0xFCC	556
Register 13:	EEPROM Size Information (EESIZE), offset 0x000	557
Register 14:	EEPROM Current Block (EEBLOCK), offset 0x004	558
Register 15:	EEPROM Current Offset (EEOFFSET), offset 0x008	559
Register 16:	EEPROM Read-Write (EERDWR), offset 0x010	
Register 17:	EEPROM Read-Write with Increment (EERDWRINC), offset 0x014	561
Register 18:	EEPROM Done Status (EEDONE), offset 0x018	562
Register 19:	EEPROM Support Control and Status (EESUPP), offset 0x01C	564
Register 20:	EEPROM Unlock (EEUNLOCK), offset 0x020	566
Register 21:	EEPROM Protection (EEPROT), offset 0x030	567
Register 22:	EEPROM Password (EEPASS0), offset 0x034	569
Register 23:	EEPROM Password (EEPASS1), offset 0x038	
Register 24:	EEPROM Password (EEPASS2), offset 0x03C	569
Register 25:	EEPROM Interrupt (EEINT), offset 0x040	
Register 26:	EEPROM Block Hide (EEHIDE), offset 0x050	
Register 27:	EEPROM Debug Mass Erase (EEDBGME), offset 0x080	
Register 28:	EEPROM Peripheral Properties (EEPROMPP), offset 0xFC0	
Register 29:	ROM Control (RMCTL), offset 0x0F0	
Register 30:	Flash Memory Protection Read Enable 0 (FMPRE0), offset 0x130 and 0x200	575

Register 31:	Flash Memory Protection Read Enable 1 (FMPRE1), offset 0x204	575
Register 32:	Flash Memory Protection Read Enable 2 (FMPRE2), offset 0x208	575
Register 33:	Flash Memory Protection Read Enable 3 (FMPRE3), offset 0x20C	575
Register 34:	Flash Memory Protection Program Enable 0 (FMPPE0), offset 0x134 and 0x400	576
Register 35:	Flash Memory Protection Program Enable 1 (FMPPE1), offset 0x404	576
Register 36:	Flash Memory Protection Program Enable 2 (FMPPE2), offset 0x408	576
Register 37:	Flash Memory Protection Program Enable 3 (FMPPE3), offset 0x40C	576
Register 38:	Boot Configuration (BOOTCFG), offset 0x1D0	578
Register 39:	User Register 0 (USER_REG0), offset 0x1E0	581
Register 40:	User Register 1 (USER_REG1), offset 0x1E4	581
Register 41:	User Register 2 (USER_REG2), offset 0x1E8	581
Register 42:	User Register 3 (USER_REG3), offset 0x1EC	581
Micro Direc	et Memory Access (µDMA)	582
Register 1:	DMA Channel Source Address End Pointer (DMASRCENDP), offset 0x000	
Register 2:	DMA Channel Destination Address End Pointer (DMADSTENDP), offset 0x004	
Register 3:	DMA Channel Control Word (DMACHCTL), offset 0x008	
Register 4:	DMA Status (DMASTAT), offset 0x000	
Register 5:	DMA Configuration (DMACFG), offset 0x004	
Register 6:	DMA Channel Control Base Pointer (DMACTLBASE), offset 0x008	
Register 7:	DMA Alternate Channel Control Base Pointer (DMAALTBASE), offset 0x00C	617
Register 8:	DMA Channel Wait-on-Request Status (DMAWAITSTAT), offset 0x010	618
Register 9:	DMA Channel Software Request (DMASWREQ), offset 0x014	
Register 10:	DMA Channel Useburst Set (DMAUSEBURSTSET), offset 0x018	620
Register 11:	DMA Channel Useburst Clear (DMAUSEBURSTCLR), offset 0x01C	621
Register 12:	DMA Channel Request Mask Set (DMAREQMASKSET), offset 0x020	
Register 13:	DMA Channel Request Mask Clear (DMAREQMASKCLR), offset 0x024	623
Register 14:	DMA Channel Enable Set (DMAENASET), offset 0x028	624
Register 15:	DMA Channel Enable Clear (DMAENACLR), offset 0x02C	625
Register 16:	DMA Channel Primary Alternate Set (DMAALTSET), offset 0x030	626
Register 17:	DMA Channel Primary Alternate Clear (DMAALTCLR), offset 0x034	627
Register 18:	DMA Channel Priority Set (DMAPRIOSET), offset 0x038	628
Register 19:	DMA Channel Priority Clear (DMAPRIOCLR), offset 0x03C	629
Register 20:	DMA Bus Error Clear (DMAERRCLR), offset 0x04C	630
Register 21:	DMA Channel Assignment (DMACHASGN), offset 0x500	631
Register 22:	DMA Channel Interrupt Status (DMACHIS), offset 0x504	632
Register 23:	DMA Channel Map Select 0 (DMACHMAP0), offset 0x510	633
Register 24:	DMA Channel Map Select 1 (DMACHMAP1), offset 0x514	634
Register 25:	DMA Channel Map Select 2 (DMACHMAP2), offset 0x518	635
Register 26:	DMA Channel Map Select 3 (DMACHMAP3), offset 0x51C	636
Register 27:	DMA Peripheral Identification 0 (DMAPeriphID0), offset 0xFE0	637
Register 28:	DMA Peripheral Identification 1 (DMAPeriphID1), offset 0xFE4	638
Register 29:	DMA Peripheral Identification 2 (DMAPeriphID2), offset 0xFE8	639
Register 30:	DMA Peripheral Identification 3 (DMAPeriphID3), offset 0xFEC	640
Register 31:	DMA Peripheral Identification 4 (DMAPeriphID4), offset 0xFD0	
Register 32:	DMA PrimeCell Identification 0 (DMAPCellID0), offset 0xFF0	642
Register 33:	DMA PrimeCell Identification 1 (DMAPCelIID1), offset 0xFF4	643
Register 34:	DMA PrimeCell Identification 2 (DMAPCelIID2), offset 0xFF8	
Register 35:	DMA PrimeCell Identification 3 (DMAPCellID3), offset 0xFFC	

General-Pur	rpose Input/Outputs (GPIOs)	646
Register 1:	GPIO Data (GPIODATA), offset 0x000	660
Register 2:	GPIO Direction (GPIODIR), offset 0x400	662
Register 3:	GPIO Interrupt Sense (GPIOIS), offset 0x404	663
Register 4:	GPIO Interrupt Both Edges (GPIOIBE), offset 0x408	664
Register 5:	GPIO Interrupt Event (GPIOIEV), offset 0x40C	665
Register 6:	GPIO Interrupt Mask (GPIOIM), offset 0x410	666
Register 7:	GPIO Raw Interrupt Status (GPIORIS), offset 0x414	667
Register 8:	GPIO Masked Interrupt Status (GPIOMIS), offset 0x418	668
Register 9:	GPIO Interrupt Clear (GPIOICR), offset 0x41C	669
Register 10:	GPIO Alternate Function Select (GPIOAFSEL), offset 0x420	670
Register 11:	GPIO 2-mA Drive Select (GPIODR2R), offset 0x500	672
Register 12:	GPIO 4-mA Drive Select (GPIODR4R), offset 0x504	673
Register 13:	GPIO 8-mA Drive Select (GPIODR8R), offset 0x508	674
Register 14:	GPIO Open Drain Select (GPIOODR), offset 0x50C	675
Register 15:	GPIO Pull-Up Select (GPIOPUR), offset 0x510	676
Register 16:	GPIO Pull-Down Select (GPIOPDR), offset 0x514	678
Register 17:	GPIO Slew Rate Control Select (GPIOSLR), offset 0x518	
Register 18:	GPIO Digital Enable (GPIODEN), offset 0x51C	681
Register 19:	GPIO Lock (GPIOLOCK), offset 0x520	683
Register 20:	GPIO Commit (GPIOCR), offset 0x524	684
Register 21:	GPIO Analog Mode Select (GPIOAMSEL), offset 0x528	686
Register 22:	GPIO Port Control (GPIOPCTL), offset 0x52C	
Register 23:	GPIO ADC Control (GPIOADCCTL), offset 0x530	690
Register 24:	GPIO DMA Control (GPIODMACTL), offset 0x534	691
Register 25:	GPIO Peripheral Identification 4 (GPIOPeriphID4), offset 0xFD0	692
Register 26:	GPIO Peripheral Identification 5 (GPIOPeriphID5), offset 0xFD4	693
Register 27:	GPIO Peripheral Identification 6 (GPIOPeriphID6), offset 0xFD8	694
Register 28:	GPIO Peripheral Identification 7 (GPIOPeriphID7), offset 0xFDC	695
Register 29:	GPIO Peripheral Identification 0 (GPIOPeriphID0), offset 0xFE0	696
Register 30:	GPIO Peripheral Identification 1 (GPIOPeriphID1), offset 0xFE4	697
Register 31:	GPIO Peripheral Identification 2 (GPIOPeriphID2), offset 0xFE8	698
Register 32:	GPIO Peripheral Identification 3 (GPIOPeriphID3), offset 0xFEC	699
Register 33:	GPIO PrimeCell Identification 0 (GPIOPCellID0), offset 0xFF0	700
Register 34:	GPIO PrimeCell Identification 1 (GPIOPCellID1), offset 0xFF4	701
Register 35:	GPIO PrimeCell Identification 2 (GPIOPCelIID2), offset 0xFF8	702
Register 36:	GPIO PrimeCell Identification 3 (GPIOPCellID3), offset 0xFFC	703
General-Pui	rpose Timers	704
Register 1:	GPTM Configuration (GPTMCFG), offset 0x000	
Register 2:	GPTM Timer A Mode (GPTMTAMR), offset 0x004	
Register 3:	GPTM Timer B Mode (GPTMTBMR), offset 0x008	
Register 4:	GPTM Control (GPTMCTL), offset 0x00C	
Register 5:	GPTM Synchronize (GPTMSYNC), offset 0x010	
Register 6:	GPTM Interrupt Mask (GPTMIMR), offset 0x018	
Register 7:	GPTM Raw Interrupt Status (GPTMRIS), offset 0x01C	
Register 8:	GPTM Masked Interrupt Status (GPTMMIS), offset 0x020	
Register 9:	GPTM Interrupt Clear (GPTMICR), offset 0x024	
Register 10:	GPTM Timer A Interval Load (GPTMTAILR) offset 0x028	

Register 11:	GPTM Timer B Interval Load (GPTMTBILR), offset 0x02C	757
Register 12:	GPTM Timer A Match (GPTMTAMATCHR), offset 0x030	758
Register 13:	GPTM Timer B Match (GPTMTBMATCHR), offset 0x034	759
Register 14:	GPTM Timer A Prescale (GPTMTAPR), offset 0x038	760
Register 15:	GPTM Timer B Prescale (GPTMTBPR), offset 0x03C	761
Register 16:	GPTM TimerA Prescale Match (GPTMTAPMR), offset 0x040	762
Register 17:	GPTM TimerB Prescale Match (GPTMTBPMR), offset 0x044	763
Register 18:	GPTM Timer A (GPTMTAR), offset 0x048	764
Register 19:	GPTM Timer B (GPTMTBR), offset 0x04C	765
Register 20:	GPTM Timer A Value (GPTMTAV), offset 0x050	766
Register 21:	GPTM Timer B Value (GPTMTBV), offset 0x054	
Register 22:	GPTM RTC Predivide (GPTMRTCPD), offset 0x058	
Register 23:	GPTM Timer A Prescale Snapshot (GPTMTAPS), offset 0x05C	
Register 24:	GPTM Timer B Prescale Snapshot (GPTMTBPS), offset 0x060	770
Register 25:	GPTM Timer A Prescale Value (GPTMTAPV), offset 0x064	771
Register 26:	GPTM Timer B Prescale Value (GPTMTBPV), offset 0x068	772
Register 27:	GPTM Peripheral Properties (GPTMPP), offset 0xFC0	773
Watchdog 1	Timers	774
Register 1:	Watchdog Load (WDTLOAD), offset 0x000	
Register 2:	Watchdog Value (WDTVALUE), offset 0x004	779
Register 3:	Watchdog Control (WDTCTL), offset 0x008	780
Register 4:	Watchdog Interrupt Clear (WDTICR), offset 0x00C	782
Register 5:	Watchdog Raw Interrupt Status (WDTRIS), offset 0x010	783
Register 6:	Watchdog Masked Interrupt Status (WDTMIS), offset 0x014	784
Register 7:	Watchdog Test (WDTTEST), offset 0x418	785
Register 8:	Watchdog Lock (WDTLOCK), offset 0xC00	786
Register 9:	Watchdog Peripheral Identification 4 (WDTPeriphID4), offset 0xFD0	787
Register 10:	Watchdog Peripheral Identification 5 (WDTPeriphID5), offset 0xFD4	788
Register 11:	Watchdog Peripheral Identification 6 (WDTPeriphID6), offset 0xFD8	789
Register 12:	Watchdog Peripheral Identification 7 (WDTPeriphID7), offset 0xFDC	790
Register 13:	Watchdog Peripheral Identification 0 (WDTPeriphID0), offset 0xFE0	791
Register 14:	Watchdog Peripheral Identification 1 (WDTPeriphID1), offset 0xFE4	792
Register 15:	Watchdog Peripheral Identification 2 (WDTPeriphID2), offset 0xFE8	793
Register 16:	Watchdog Peripheral Identification 3 (WDTPeriphID3), offset 0xFEC	794
Register 17:	Watchdog PrimeCell Identification 0 (WDTPCellID0), offset 0xFF0	795
Register 18:	Watchdog PrimeCell Identification 1 (WDTPCellID1), offset 0xFF4	
Register 19:	Watchdog PrimeCell Identification 2 (WDTPCellID2), offset 0xFF8	797
Register 20:	Watchdog PrimeCell Identification 3 (WDTPCellID3), offset 0xFFC	798
Analog-to-D	Digital Converter (ADC)	799
Register 1:	ADC Active Sample Sequencer (ADCACTSS), offset 0x000	
Register 2:	ADC Raw Interrupt Status (ADCRIS), offset 0x004	823
Register 3:	ADC Interrupt Mask (ADCIM), offset 0x008	
Register 4:	ADC Interrupt Status and Clear (ADCISC), offset 0x00C	828
Register 5:	ADC Overflow Status (ADCOSTAT), offset 0x010	
Register 6:	ADC Event Multiplexer Select (ADCEMUX), offset 0x014	
Register 7:	ADC Underflow Status (ADCUSTAT), offset 0x018	
Register 8:	ADC Trigger Source Select (ADCTSSEL), offset 0x01C	839
Register 9:	ADC Sample Sequencer Priority (ADCSSPRI), offset 0x020	

Register 10:	ADC Sample Phase Control (ADCSPC), offset 0x024	843
Register 11:	ADC Processor Sample Sequence Initiate (ADCPSSI), offset 0x028	845
Register 12:	ADC Sample Averaging Control (ADCSAC), offset 0x030	847
Register 13:	ADC Digital Comparator Interrupt Status and Clear (ADCDCISC), offset 0x034	848
Register 14:	ADC Control (ADCCTL), offset 0x038	850
Register 15:	ADC Sample Sequence Input Multiplexer Select 0 (ADCSSMUX0), offset 0x040	851
Register 16:	ADC Sample Sequence Control 0 (ADCSSCTL0), offset 0x044	853
Register 17:	ADC Sample Sequence Result FIFO 0 (ADCSSFIFO0), offset 0x048	860
Register 18:	ADC Sample Sequence Result FIFO 1 (ADCSSFIFO1), offset 0x068	860
Register 19:	ADC Sample Sequence Result FIFO 2 (ADCSSFIFO2), offset 0x088	860
Register 20:	ADC Sample Sequence Result FIFO 3 (ADCSSFIFO3), offset 0x0A8	860
Register 21:	ADC Sample Sequence FIFO 0 Status (ADCSSFSTAT0), offset 0x04C	861
Register 22:	ADC Sample Sequence FIFO 1 Status (ADCSSFSTAT1), offset 0x06C	861
Register 23:	ADC Sample Sequence FIFO 2 Status (ADCSSFSTAT2), offset 0x08C	861
Register 24:	ADC Sample Sequence FIFO 3 Status (ADCSSFSTAT3), offset 0x0AC	861
Register 25:	ADC Sample Sequence 0 Operation (ADCSSOP0), offset 0x050	863
Register 26:	ADC Sample Sequence 0 Digital Comparator Select (ADCSSDC0), offset 0x054	
Register 27:	ADC Sample Sequence Extended Input Multiplexer Select 0 (ADCSSEMUX0), offset 0x058	
Register 28:	ADC Sample Sequence Input Multiplexer Select 1 (ADCSSMUX1), offset 0x060	
Register 29:	ADC Sample Sequence Input Multiplexer Select 1 (ADCSSMUX1), offset 0x000	
Register 30:	ADC Sample Sequence Control 1 (ADCSSCTL1), offset 0x064	
Register 31:	ADC Sample Sequence Control 1 (ADCSSCTL1), offset 0x004	
•	· · · · · · · · · · · · · · · · · · ·	
Register 32:	ADC Sample Sequence 1 Operation (ADCSSOP1), offset 0x070	
Register 33:	ADC Sample Sequence 1 Digital Comparator Select (ADCSSDC1), offset 0x074	
Register 34:		
Register 35:	ADC Sample Sequence 2 Digital Comparator Select (ADCSSDC2), offset 0x094	0/0
Register 36:	ADC Sample Sequence Extended Input Multiplexer Select 1 (ADCSSEMUX1), offset 0x078	877
Register 37:	ADC Sample Sequence Extended Input Multiplexer Select 2 (ADCSSEMUX2), offset 0x098	
Register 38:	ADC Sample Sequence Input Multiplexer Select 3 (ADCSSMUX3), offset 0x0A0	
Register 39:	ADC Sample Sequence Control 3 (ADCSSCTL3), offset 0x0A4	
Register 40:	ADC Sample Sequence 3 Operation (ADCSSOP3), offset 0x080	
Register 41:	ADC Sample Sequence 3 Digital Comparator Select (ADCSSDC3), offset 0x0B4	
Register 42:	ADC Sample Sequence Extended Input Multiplexer Select 3 (ADCSSEMUX3), offset	
Dogiotor 42.	0x0B8	
Register 43:	ADC Digital Comparator Reset Initial Conditions (ADCDCRIC), offset 0xD00	
Register 44:	ADC Digital Comparator Control 0 (ADCDCCTL0), offset 0xE00	
Register 45:	ADC Digital Comparator Control 1 (ADCDCCTL1), offset 0xE04	
Register 46:	ADC Digital Comparator Control 2 (ADCDCCTL2), offset 0xE08	
Register 47:	ADC Digital Comparator Control 3 (ADCDCCTL3), offset 0xE0C	
Register 48:	ADC Digital Comparator Control 4 (ADCDCCTL4), offset 0xE10	
Register 49:	ADC Digital Comparator Control 5 (ADCDCCTL5), offset 0xE14	
Register 50:	ADC Digital Comparator Control 6 (ADCDCCTL6), offset 0xE18	
Register 51:	ADC Digital Comparator Control 7 (ADCDCCTL7), offset 0xE1C	
Register 52:	ADC Digital Comparator Range 0 (ADCDCCMP0), offset 0xE40	
Register 53:	ADC Digital Comparator Range 2 (ADCDCCMP1), offset 0xE44	893 893
Register 54:	AUG DIGIJA COMBARATOR KANDE Z (AUGUCUMPZ) OTISET UYEAX	XUX

Register 55:	ADC Digital Comparator Range 3 (ADCDCCMP3), offset 0xE4C	893
Register 56:	ADC Digital Comparator Range 4 (ADCDCCMP4), offset 0xE50	893
Register 57:	ADC Digital Comparator Range 5 (ADCDCCMP5), offset 0xE54	893
Register 58:	ADC Digital Comparator Range 6 (ADCDCCMP6), offset 0xE58	893
Register 59:	ADC Digital Comparator Range 7 (ADCDCCMP7), offset 0xE5C	893
Register 60:	ADC Peripheral Properties (ADCPP), offset 0xFC0	894
Register 61:	ADC Peripheral Configuration (ADCPC), offset 0xFC4	896
Register 62:	ADC Clock Configuration (ADCCC), offset 0xFC8	897
Universal A	synchronous Receivers/Transmitters (UARTs)	898
Register 1:	UART Data (UARTDR), offset 0x000	
Register 2:	UART Receive Status/Error Clear (UARTRSR/UARTECR), offset 0x004	
Register 3:	UART Flag (UARTFR), offset 0x018	
Register 4:	UART IrDA Low-Power Register (UARTILPR), offset 0x020	919
Register 5:	UART Integer Baud-Rate Divisor (UARTIBRD), offset 0x024	920
Register 6:	UART Fractional Baud-Rate Divisor (UARTFBRD), offset 0x028	921
Register 7:	UART Line Control (UARTLCRH), offset 0x02C	922
Register 8:	UART Control (UARTCTL), offset 0x030	924
Register 9:	UART Interrupt FIFO Level Select (UARTIFLS), offset 0x034	928
Register 10:	UART Interrupt Mask (UARTIM), offset 0x038	930
Register 11:	UART Raw Interrupt Status (UARTRIS), offset 0x03C	933
Register 12:	UART Masked Interrupt Status (UARTMIS), offset 0x040	936
Register 13:	UART Interrupt Clear (UARTICR), offset 0x044	939
Register 14:	UART DMA Control (UARTDMACTL), offset 0x048	941
Register 15:	UART 9-Bit Self Address (UART9BITADDR), offset 0x0A4	942
Register 16:	UART 9-Bit Self Address Mask (UART9BITAMASK), offset 0x0A8	943
Register 17:	UART Peripheral Properties (UARTPP), offset 0xFC0	944
Register 18:	UART Clock Configuration (UARTCC), offset 0xFC8	945
Register 19:	UART Peripheral Identification 4 (UARTPeriphID4), offset 0xFD0	946
Register 20:	UART Peripheral Identification 5 (UARTPeriphID5), offset 0xFD4	947
Register 21:	UART Peripheral Identification 6 (UARTPeriphID6), offset 0xFD8	
Register 22:	UART Peripheral Identification 7 (UARTPeriphID7), offset 0xFDC	949
Register 23:	UART Peripheral Identification 0 (UARTPeriphID0), offset 0xFE0	950
Register 24:	UART Peripheral Identification 1 (UARTPeriphID1), offset 0xFE4	951
Register 25:	UART Peripheral Identification 2 (UARTPeriphID2), offset 0xFE8	952
Register 26:	UART Peripheral Identification 3 (UARTPeriphID3), offset 0xFEC	953
Register 27:	UART PrimeCell Identification 0 (UARTPCellID0), offset 0xFF0	
Register 28:	UART PrimeCell Identification 1 (UARTPCellID1), offset 0xFF4	955
Register 29:	UART PrimeCell Identification 2 (UARTPCellID2), offset 0xFF8	956
Register 30:	UART PrimeCell Identification 3 (UARTPCellID3), offset 0xFFC	957
Synchrono	us Serial Interface (SSI)	958
Register 1:	SSI Control 0 (SSICR0), offset 0x000	
Register 2:	SSI Control 1 (SSICR1), offset 0x004	
Register 3:	SSI Data (SSIDR), offset 0x008	
Register 4:	SSI Status (SSISR), offset 0x00C	
Register 5:	SSI Clock Prescale (SSICPSR), offset 0x010	
Register 6:	SSI Interrupt Mask (SSIIM), offset 0x014	
Register 7:	SSI Raw Interrupt Status (SSIRIS), offset 0x018	
Register 8:	SSI Masked Interrupt Status (SSIMIS), offset 0x01C	

Register 9:	SSI Interrupt Clear (SSIICR), offset 0x020	987
Register 10:	SSI DMA Control (SSIDMACTL), offset 0x024	988
Register 11:	SSI Clock Configuration (SSICC), offset 0xFC8	
Register 12:	SSI Peripheral Identification 4 (SSIPeriphID4), offset 0xFD0	990
Register 13:	SSI Peripheral Identification 5 (SSIPeriphID5), offset 0xFD4	991
Register 14:	SSI Peripheral Identification 6 (SSIPeriphID6), offset 0xFD8	992
Register 15:	SSI Peripheral Identification 7 (SSIPeriphID7), offset 0xFDC	993
Register 16:	SSI Peripheral Identification 0 (SSIPeriphID0), offset 0xFE0	
Register 17:	SSI Peripheral Identification 1 (SSIPeriphID1), offset 0xFE4	
Register 18:	SSI Peripheral Identification 2 (SSIPeriphID2), offset 0xFE8	
Register 19:	SSI Peripheral Identification 3 (SSIPeriphID3), offset 0xFEC	
Register 20:	SSI PrimeCell Identification 0 (SSIPCellID0), offset 0xFF0	
Register 21:	SSI PrimeCell Identification 1 (SSIPCelIID1), offset 0xFF4	
Register 22:	SSI PrimeCell Identification 2 (SSIPCelIID2), offset 0xFF8	
Register 23:	SSI PrimeCell Identification 3 (SSIPCelIID3), offset 0xFFC	
Inter-Integr	ated Circuit (I ² C) Interface	1002
Register 1:	I ² C Master Slave Address (I2CMSA), offset 0x000	1024
Register 2:	I ² C Master Control/Status (I2CMCS), offset 0x004	1025
Register 3:	I ² C Master Data (I2CMDR), offset 0x008	1030
Register 4:	I ² C Master Timer Period (I2CMTPR), offset 0x00C	1031
Register 5:	I ² C Master Interrupt Mask (I2CMIMR), offset 0x010	1032
Register 6:	I ² C Master Raw Interrupt Status (I2CMRIS), offset 0x014	1033
Register 7:	I ² C Master Masked Interrupt Status (I2CMMIS), offset 0x018	1034
Register 8:	I ² C Master Interrupt Clear (I2CMICR), offset 0x01C	
Register 9:	I ² C Master Configuration (I2CMCR), offset 0x020	
Register 10:	I ² C Master Clock Low Timeout Count (I2CMCLKOCNT), offset 0x024	
Register 11:	I ² C Master Bus Monitor (I2CMBMON), offset 0x02C	
Register 12:	I ² C Master Configuration 2 (I2CMCR2), offset 0x038	
Register 13:	I ² C Slave Own Address (I2CSOAR), offset 0x800	
Register 14:	I ² C Slave Control/Status (I2CSCSR), offset 0x804	
Register 15:	I ² C Slave Data (I2CSDR), offset 0x808	
Register 16:	I ² C Slave Interrupt Mask (I2CSIMR), offset 0x80C	
Register 17:	I ² C Slave Raw Interrupt Status (I2CSRIS), offset 0x810	
Register 18:	I ² C Slave Masked Interrupt Status (I2CSMIS), offset 0x814	
Register 19:	I ² C Slave Interrupt Clear (I2CSICR), offset 0x818	
Register 20:	I ² C Slave Own Address 2 (I2CSOAR2), offset 0x81C	
Register 21:	I ² C Slave ACK Control (I2CSACKCTL), offset 0x820	
Register 22:	I ² C Peripheral Properties (I2CPP), offset 0xFC0	
Register 23:	I ² C Peripheral Configuration (I2CPC), offset 0xFC4	
_	Area Network (CAN) Module	
Register 1:	CAN Control (CANCTL), offset 0x000	1035
Register 2:	CAN Status (CANSTS), offset 0x004	
Register 3:	CAN Error Counter (CANERR), offset 0x008	
Register 4:	CAN Bit Timing (CANBIT), offset 0x00C	
Register 5:	CAN Interrupt (CANINT), offset 0x010	
Register 6:	CAN Test (CANTST), offset 0x014	
Register 7	CAN Baud Rate Prescaler Extension (CANBRPE) offset 0x018	

Register 8:	CAN IF1 Command Request (CANIF1CRQ), offset 0x020	1086
Register 9:	CAN IF2 Command Request (CANIF2CRQ), offset 0x080	1086
Register 10:	CAN IF1 Command Mask (CANIF1CMSK), offset 0x024	1087
Register 11:	CAN IF2 Command Mask (CANIF2CMSK), offset 0x084	1087
Register 12:	CAN IF1 Mask 1 (CANIF1MSK1), offset 0x028	1090
Register 13:	CAN IF2 Mask 1 (CANIF2MSK1), offset 0x088	1090
Register 14:	CAN IF1 Mask 2 (CANIF1MSK2), offset 0x02C	1091
Register 15:	CAN IF2 Mask 2 (CANIF2MSK2), offset 0x08C	1091
Register 16:	CAN IF1 Arbitration 1 (CANIF1ARB1), offset 0x030	1093
Register 17:	CAN IF2 Arbitration 1 (CANIF2ARB1), offset 0x090	1093
Register 18:	CAN IF1 Arbitration 2 (CANIF1ARB2), offset 0x034	
Register 19:	CAN IF2 Arbitration 2 (CANIF2ARB2), offset 0x094	1094
Register 20:	CAN IF1 Message Control (CANIF1MCTL), offset 0x038	1096
Register 21:	CAN IF2 Message Control (CANIF2MCTL), offset 0x098	
Register 22:	CAN IF1 Data A1 (CANIF1DA1), offset 0x03C	
Register 23:	CAN IF1 Data A2 (CANIF1DA2), offset 0x040	1099
Register 24:	CAN IF1 Data B1 (CANIF1DB1), offset 0x044	
Register 25:	CAN IF1 Data B2 (CANIF1DB2), offset 0x048	
Register 26:	CAN IF2 Data A1 (CANIF2DA1), offset 0x09C	
Register 27:	CAN IF2 Data A2 (CANIF2DA2), offset 0x0A0	
Register 28:	CAN IF2 Data B1 (CANIF2DB1), offset 0x0A4	
Register 29:	CAN IF2 Data B2 (CANIF2DB2), offset 0x0A8	
Register 30:	CAN Transmission Request 1 (CANTXRQ1), offset 0x100	
Register 31:	CAN Transmission Request 2 (CANTXRQ2), offset 0x104	
Register 32:	CAN New Data 1 (CANNWDA1), offset 0x120	
Register 33:	CAN New Data 2 (CANNWDA2), offset 0x124	
Register 34:	CAN Message 1 Interrupt Pending (CANMSG1INT), offset 0x140	
Register 35:	CAN Message 2 Interrupt Pending (CANMSG2INT), offset 0x144	
Register 36:	CAN Message 1 Valid (CANMSG1VAL), offset 0x160	
Register 37:	CAN Message 2 Valid (CANMSG2VAL), offset 0x164	
=	erial Bus (USB) Controller	
Register 1:	USB Device Functional Address (USBFADDR), offset 0x000	
Register 2:	USB Power (USBPOWER), offset 0x001	
Register 3:	USB Transmit Interrupt Status (USBTXIS), offset 0x002	
Register 4:	USB Receive Interrupt Status (USBRXIS), offset 0x004	
Register 5:	USB Transmit Interrupt Enable (USBTXIE), offset 0x006	
Register 6:	USB Receive Interrupt Enable (USBRXIE), offset 0x008	
Register 7:	USB General Interrupt Status (USBIS), offset 0x00A	
Register 8:	USB Interrupt Enable (USBIE), offset 0x00B	
Register 9:	USB Frame Value (USBFRAME), offset 0x00C	
Register 5.	USB Endpoint Index (USBEPIDX), offset 0x00E	
Register 11:	USB Test Mode (USBTEST), offset 0x00F	
Register 12:	USB FIFO Endpoint 0 (USBFIFO0), offset 0x020	
Register 13:	USB FIFO Endpoint 1 (USBFIFO1), offset 0x024	
Register 14:	USB FIFO Endpoint 2 (USBFIFO2), offset 0x028	
Register 15:	USB FIFO Endpoint 3 (USBFIFO2), offset 0x02C	
•	USB FIFO Endpoint 4 (USBFIFO4), offset 0x030	
Register 16:	USB FIFO Endpoint 4 (USBFIFO4), offset 0x030	1140 1146
	CONTROL OF THE HOLDON IN THE CONTROL ON SEL UXUA4	1140

Register 18:	USB FIFO Endpoint 6 (USBFIFO6), offset 0x038	1146
Register 19:	USB FIFO Endpoint 7 (USBFIFO7), offset 0x03C	1146
Register 20:	USB Device Control (USBDEVCTL), offset 0x060	1147
Register 21:	USB Transmit Dynamic FIFO Sizing (USBTXFIFOSZ), offset 0x062	1149
Register 22:	USB Receive Dynamic FIFO Sizing (USBRXFIFOSZ), offset 0x063	1149
Register 23:	USB Transmit FIFO Start Address (USBTXFIFOADD), offset 0x064	1150
Register 24:	USB Receive FIFO Start Address (USBRXFIFOADD), offset 0x066	1150
Register 25:	USB Connect Timing (USBCONTIM), offset 0x07A	
Register 26:	USB OTG VBUS Pulse Timing (USBVPLEN), offset 0x07B	1152
Register 27:	USB Full-Speed Last Transaction to End of Frame Timing (USBFSEOF), offset 0x07D	
Register 28:	USB Low-Speed Last Transaction to End of Frame Timing (USBLSEOF), offset 0x07E	1154
Register 29:	USB Transmit Functional Address Endpoint 0 (USBTXFUNCADDR0), offset 0x080	1155
Register 30:	USB Transmit Functional Address Endpoint 1 (USBTXFUNCADDR1), offset 0x088	1155
Register 31:	USB Transmit Functional Address Endpoint 2 (USBTXFUNCADDR2), offset 0x090	1155
Register 32:	USB Transmit Functional Address Endpoint 3 (USBTXFUNCADDR3), offset 0x098	
Register 33:	USB Transmit Functional Address Endpoint 4 (USBTXFUNCADDR4), offset 0x0A0	1155
Register 34:	USB Transmit Functional Address Endpoint 5 (USBTXFUNCADDR5), offset 0x0A8	1155
Register 35:	USB Transmit Functional Address Endpoint 6 (USBTXFUNCADDR6), offset 0x0B0	1155
Register 36:	USB Transmit Functional Address Endpoint 7 (USBTXFUNCADDR7), offset 0x0B8	1155
Register 37:	USB Transmit Hub Address Endpoint 0 (USBTXHUBADDR0), offset 0x082	1156
Register 38:	USB Transmit Hub Address Endpoint 1 (USBTXHUBADDR1), offset 0x08A	1156
Register 39:	USB Transmit Hub Address Endpoint 2 (USBTXHUBADDR2), offset 0x092	1156
Register 40:	USB Transmit Hub Address Endpoint 3 (USBTXHUBADDR3), offset 0x09A	1156
Register 41:	USB Transmit Hub Address Endpoint 4 (USBTXHUBADDR4), offset 0x0A2	1156
Register 42:	USB Transmit Hub Address Endpoint 5 (USBTXHUBADDR5), offset 0x0AA	1156
Register 43:	USB Transmit Hub Address Endpoint 6 (USBTXHUBADDR6), offset 0x0B2	1156
Register 44:	USB Transmit Hub Address Endpoint 7 (USBTXHUBADDR7), offset 0x0BA	1156
Register 45:	USB Transmit Hub Port Endpoint 0 (USBTXHUBPORT0), offset 0x083	1157
Register 46:	USB Transmit Hub Port Endpoint 1 (USBTXHUBPORT1), offset 0x08B	1157
Register 47:	USB Transmit Hub Port Endpoint 2 (USBTXHUBPORT2), offset 0x093	1157
Register 48:	USB Transmit Hub Port Endpoint 3 (USBTXHUBPORT3), offset 0x09B	1157
Register 49:	USB Transmit Hub Port Endpoint 4 (USBTXHUBPORT4), offset 0x0A3	1157
Register 50:	USB Transmit Hub Port Endpoint 5 (USBTXHUBPORT5), offset 0x0AB	
Register 51:	USB Transmit Hub Port Endpoint 6 (USBTXHUBPORT6), offset 0x0B3	
Register 52:	USB Transmit Hub Port Endpoint 7 (USBTXHUBPORT7), offset 0x0BB	
Register 53:	USB Receive Functional Address Endpoint 1 (USBRXFUNCADDR1), offset 0x08C	
Register 54:	USB Receive Functional Address Endpoint 2 (USBRXFUNCADDR2), offset 0x094	
Register 55:	USB Receive Functional Address Endpoint 3 (USBRXFUNCADDR3), offset 0x09C	
Register 56:	USB Receive Functional Address Endpoint 4 (USBRXFUNCADDR4), offset 0x0A4	
Register 57:	USB Receive Functional Address Endpoint 5 (USBRXFUNCADDR5), offset 0x0AC	1158
Register 58:	USB Receive Functional Address Endpoint 6 (USBRXFUNCADDR6), offset 0x0B4	1158
Register 59:	USB Receive Functional Address Endpoint 7 (USBRXFUNCADDR7), offset 0x0BC	
Register 60:	USB Receive Hub Address Endpoint 1 (USBRXHUBADDR1), offset 0x08E	
Register 61:	USB Receive Hub Address Endpoint 2 (USBRXHUBADDR2), offset 0x096	
Register 62:	USB Receive Hub Address Endpoint 3 (USBRXHUBADDR3), offset 0x09E	
Register 63:	USB Receive Hub Address Endpoint 4 (USBRXHUBADDR4), offset 0x0A6	
Register 64:	USB Receive Hub Address Endpoint 5 (USBRXHUBADDR5), offset 0x0AE	1159
Register 65:	USB Receive Hub Address Endpoint 6 (USBRXHUBADDR6), offset 0x0B6	1159

Register 66:	USB Receive Hub Address Endpoint / (USBRXHUBADDR7), offset 0x0BE	. 1159
Register 67:	USB Receive Hub Port Endpoint 1 (USBRXHUBPORT1), offset 0x08F	
Register 68:	USB Receive Hub Port Endpoint 2 (USBRXHUBPORT2), offset 0x097	. 1160
Register 69:	USB Receive Hub Port Endpoint 3 (USBRXHUBPORT3), offset 0x09F	. 1160
Register 70:	USB Receive Hub Port Endpoint 4 (USBRXHUBPORT4), offset 0x0A7	. 1160
Register 71:	USB Receive Hub Port Endpoint 5 (USBRXHUBPORT5), offset 0x0AF	. 1160
Register 72:	USB Receive Hub Port Endpoint 6 (USBRXHUBPORT6), offset 0x0B7	. 1160
Register 73:	USB Receive Hub Port Endpoint 7 (USBRXHUBPORT7), offset 0x0BF	. 1160
Register 74:	USB Maximum Transmit Data Endpoint 1 (USBTXMAXP1), offset 0x110	. 1161
Register 75:	USB Maximum Transmit Data Endpoint 2 (USBTXMAXP2), offset 0x120	. 1161
Register 76:	USB Maximum Transmit Data Endpoint 3 (USBTXMAXP3), offset 0x130	. 1161
Register 77:	USB Maximum Transmit Data Endpoint 4 (USBTXMAXP4), offset 0x140	. 1161
Register 78:	USB Maximum Transmit Data Endpoint 5 (USBTXMAXP5), offset 0x150	. 1161
Register 79:	USB Maximum Transmit Data Endpoint 6 (USBTXMAXP6), offset 0x160	. 1161
Register 80:	USB Maximum Transmit Data Endpoint 7 (USBTXMAXP7), offset 0x170	. 1161
Register 81:	USB Control and Status Endpoint 0 Low (USBCSRL0), offset 0x102	. 1162
Register 82:	USB Control and Status Endpoint 0 High (USBCSRH0), offset 0x103	. 1166
Register 83:	USB Receive Byte Count Endpoint 0 (USBCOUNT0), offset 0x108	. 1168
Register 84:	USB Type Endpoint 0 (USBTYPE0), offset 0x10A	. 1169
Register 85:	USB NAK Limit (USBNAKLMT), offset 0x10B	. 1170
Register 86:	USB Transmit Control and Status Endpoint 1 Low (USBTXCSRL1), offset 0x112	. 1171
Register 87:	USB Transmit Control and Status Endpoint 2 Low (USBTXCSRL2), offset 0x122	. 1171
Register 88:	USB Transmit Control and Status Endpoint 3 Low (USBTXCSRL3), offset 0x132	. 1171
Register 89:	USB Transmit Control and Status Endpoint 4 Low (USBTXCSRL4), offset 0x142	. 1171
Register 90:	USB Transmit Control and Status Endpoint 5 Low (USBTXCSRL5), offset 0x152	. 1171
Register 91:	USB Transmit Control and Status Endpoint 6 Low (USBTXCSRL6), offset 0x162	. 1171
Register 92:	USB Transmit Control and Status Endpoint 7 Low (USBTXCSRL7), offset 0x172	. 1171
Register 93:	USB Transmit Control and Status Endpoint 1 High (USBTXCSRH1), offset 0x113	. 1175
Register 94:	USB Transmit Control and Status Endpoint 2 High (USBTXCSRH2), offset 0x123	. 1175
Register 95:	USB Transmit Control and Status Endpoint 3 High (USBTXCSRH3), offset 0x133	. 1175
Register 96:	USB Transmit Control and Status Endpoint 4 High (USBTXCSRH4), offset 0x143	. 1175
Register 97:	USB Transmit Control and Status Endpoint 5 High (USBTXCSRH5), offset 0x153	. 1175
Register 98:	USB Transmit Control and Status Endpoint 6 High (USBTXCSRH6), offset 0x163	. 1175
Register 99:	USB Transmit Control and Status Endpoint 7 High (USBTXCSRH7), offset 0x173	. 1175
Register 100:	USB Maximum Receive Data Endpoint 1 (USBRXMAXP1), offset 0x114	. 1179
Register 101:	USB Maximum Receive Data Endpoint 2 (USBRXMAXP2), offset 0x124	. 1179
Register 102:	USB Maximum Receive Data Endpoint 3 (USBRXMAXP3), offset 0x134	. 1179
Register 103:	USB Maximum Receive Data Endpoint 4 (USBRXMAXP4), offset 0x144	. 1179
Register 104:	USB Maximum Receive Data Endpoint 5 (USBRXMAXP5), offset 0x154	. 1179
Register 105:	USB Maximum Receive Data Endpoint 6 (USBRXMAXP6), offset 0x164	. 1179
Register 106:	USB Maximum Receive Data Endpoint 7 (USBRXMAXP7), offset 0x174	. 1179
Register 107:	USB Receive Control and Status Endpoint 1 Low (USBRXCSRL1), offset 0x116	. 1180
Register 108:	USB Receive Control and Status Endpoint 2 Low (USBRXCSRL2), offset 0x126	. 1180
Register 109:	USB Receive Control and Status Endpoint 3 Low (USBRXCSRL3), offset 0x136	. 1180
Register 110:	USB Receive Control and Status Endpoint 4 Low (USBRXCSRL4), offset 0x146	. 1180
Register 111:	USB Receive Control and Status Endpoint 5 Low (USBRXCSRL5), offset 0x156	. 1180
Register 112:	USB Receive Control and Status Endpoint 6 Low (USBRXCSRL6), offset 0x166	. 1180
Register 113:	USB Receive Control and Status Endpoint 7 Low (USBRXCSRL7), offset 0x176	. 1180

Register 114:	USB Receive Control and Status Endpoint 1 High (USBRXCSRH1), offset 0x117	1185
Register 115:	USB Receive Control and Status Endpoint 2 High (USBRXCSRH2), offset 0x127	1185
Register 116:	USB Receive Control and Status Endpoint 3 High (USBRXCSRH3), offset 0x137	1185
Register 117:	USB Receive Control and Status Endpoint 4 High (USBRXCSRH4), offset 0x147	1185
Register 118:	USB Receive Control and Status Endpoint 5 High (USBRXCSRH5), offset 0x157	1185
Register 119:	USB Receive Control and Status Endpoint 6 High (USBRXCSRH6), offset 0x167	1185
Register 120:	USB Receive Control and Status Endpoint 7 High (USBRXCSRH7), offset 0x177	1185
Register 121:	USB Receive Byte Count Endpoint 1 (USBRXCOUNT1), offset 0x118	1189
Register 122:	USB Receive Byte Count Endpoint 2 (USBRXCOUNT2), offset 0x128	1189
Register 123:	USB Receive Byte Count Endpoint 3 (USBRXCOUNT3), offset 0x138	1189
Register 124:	USB Receive Byte Count Endpoint 4 (USBRXCOUNT4), offset 0x148	1189
-	USB Receive Byte Count Endpoint 5 (USBRXCOUNT5), offset 0x158	
	USB Receive Byte Count Endpoint 6 (USBRXCOUNT6), offset 0x168	
	USB Receive Byte Count Endpoint 7 (USBRXCOUNT7), offset 0x178	
	USB Host Transmit Configure Type Endpoint 1 (USBTXTYPE1), offset 0x11A	
	USB Host Transmit Configure Type Endpoint 2 (USBTXTYPE2), offset 0x12A	
	USB Host Transmit Configure Type Endpoint 3 (USBTXTYPE3), offset 0x13A	
	USB Host Transmit Configure Type Endpoint 4 (USBTXTYPE4), offset 0x14A	
	USB Host Transmit Configure Type Endpoint 5 (USBTXTYPE5), offset 0x15A	
-	USB Host Transmit Configure Type Endpoint 6 (USBTXTYPE6), offset 0x16A	
-	USB Host Transmit Configure Type Endpoint 7 (USBTXTYPE7), offset 0x17A	
_	USB Host Transmit Interval Endpoint 1 (USBTXINTERVAL1), offset 0x11B	
-	USB Host Transmit Interval Endpoint 2 (USBTXINTERVAL2), offset 0x12B	
-	USB Host Transmit Interval Endpoint 3 (USBTXINTERVAL3), offset 0x13B	
	USB Host Transmit Interval Endpoint 4 (USBTXINTERVAL4), offset 0x14B	
_	USB Host Transmit Interval Endpoint 5 (USBTXINTERVAL5), offset 0x15B	
-	USB Host Transmit Interval Endpoint 6 (USBTXINTERVAL6), offset 0x16B	
	USB Host Transmit Interval Endpoint 7 (USBTXINTERVAL7), offset 0x17B	
	USB Host Configure Receive Type Endpoint 1 (USBRXTYPE1), offset 0x11C	
	USB Host Configure Receive Type Endpoint 2 (USBRXTYPE2), offset 0x12C	
	USB Host Configure Receive Type Endpoint 3 (USBRXTYPE3), offset 0x13C	
	USB Host Configure Receive Type Endpoint 4 (USBRXTYPE4), offset 0x14C	
	USB Host Configure Receive Type Endpoint 5 (USBRXTYPE6), offset 0x16C	
_	USB Host Configure Receive Type Endpoint 7 (USBRXTYPE7), offset 0x17C	
	USB Host Receive Polling Interval Endpoint 1 (USBRXINTERVAL1), offset 0x11D	
-	USB Host Receive Polling Interval Endpoint 2 (USBRXINTERVAL2), offset 0x12D	
•	USB Host Receive Polling Interval Endpoint 3 (USBRXINTERVAL3), offset 0x13D	
•	USB Host Receive Polling Interval Endpoint 4 (USBRXINTERVAL4), offset 0x14D	
-	USB Host Receive Polling Interval Endpoint 5 (USBRXINTERVAL5), offset 0x15D	
-	USB Host Receive Polling Interval Endpoint 6 (USBRXINTERVAL6), offset 0x16D	
-	USB Host Receive Polling Interval Endpoint 7 (USBRXINTERVAL7), offset 0x17D	
-	USB Request Packet Count in Block Transfer Endpoint 1 (USBRQPKTCOUNT1), offset	
. 5	0x304	1196
Register 157:	USB Request Packet Count in Block Transfer Endpoint 2 (USBRQPKTCOUNT2), offset 0x308	
Register 158:	USB Request Packet Count in Block Transfer Endpoint 3 (USBRQPKTCOUNT3), offset	4400

Register 159:	USB Request Packet Count in Block Transfer Endpoint 4 (USBRQPKTCOUNT4), offset 0x310	1196
Register 160:	USB Request Packet Count in Block Transfer Endpoint 5 (USBRQPKTCOUNT5), offset 0x314	
Register 161:	USB Request Packet Count in Block Transfer Endpoint 6 (USBRQPKTCOUNT6), offset 0x318	
Register 162:	USB Request Packet Count in Block Transfer Endpoint 7 (USBRQPKTCOUNT7), offset 0x31C	
Register 163:	USB Receive Double Packet Buffer Disable (USBRXDPKTBUFDIS), offset 0x340	
Register 164:	USB Transmit Double Packet Buffer Disable (USBTXDPKTBUFDIS), offset 0x342	. 1198
Register 165:	USB External Power Control (USBEPC), offset 0x400	1199
Register 166:	USB External Power Control Raw Interrupt Status (USBEPCRIS), offset 0x404	. 1202
Register 167:	USB External Power Control Interrupt Mask (USBEPCIM), offset 0x408	1203
Register 168:	USB External Power Control Interrupt Status and Clear (USBEPCISC), offset 0x40C	. 1204
Register 169:	USB Device RESUME Raw Interrupt Status (USBDRRIS), offset 0x410	1205
Register 170:	USB Device RESUME Interrupt Mask (USBDRIM), offset 0x414	1206
	USB Device RESUME Interrupt Status and Clear (USBDRISC), offset 0x418	
•	USB General-Purpose Control and Status (USBGPCS), offset 0x41C	
Register 173:	USB VBUS Droop Control (USBVDC), offset 0x430	1209
-	USB VBUS Droop Control Raw Interrupt Status (USBVDCRIS), offset 0x434	
	USB VBUS Droop Control Interrupt Mask (USBVDCIM), offset 0x438	
	USB VBUS Droop Control Interrupt Status and Clear (USBVDCISC), offset 0x43C	
-	USB ID Valid Detect Raw Interrupt Status (USBIDVRIS), offset 0x444	
	USB ID Valid Detect Interrupt Mask (USBIDVIM), offset 0x448	
	USB ID Valid Detect Interrupt Status and Clear (USBIDVISC), offset 0x44C	
-	USB DMA Select (USBDMASEL), offset 0x450	
Register 181:	USB Peripheral Properties (USBPP), offset 0xFC0	1218
Analog Con	nparators	1219
Register 1:	Analog Comparator Masked Interrupt Status (ACMIS), offset 0x000	1226
Register 2:	Analog Comparator Raw Interrupt Status (ACRIS), offset 0x004	
Register 3:	Analog Comparator Interrupt Enable (ACINTEN), offset 0x008	
Register 4:	Analog Comparator Reference Voltage Control (ACREFCTL), offset 0x010	
Register 5:	Analog Comparator Status 0 (ACSTAT0), offset 0x020	
Register 6:	Analog Comparator Status 1 (ACSTAT1), offset 0x040	
Register 7:	Analog Comparator Status 2 (ACSTAT2), offset 0x060	
Register 8:	Analog Comparator Control 0 (ACCTL0), offset 0x024	
Register 9:	Analog Comparator Control 1 (ACCTL1), offset 0x044	
Register 10:	Analog Comparator Control 2 (ACCTL2), offset 0x064	
Register 11:	Analog Comparator Peripheral Properties (ACMPPP), offset 0xFC0	. 1233
Pulse Width	Modulator (PWM)	
Register 1:	PWM Master Control (PWMCTL), offset 0x000	1249
Register 2:	PWM Time Base Sync (PWMSYNC), offset 0x004	
Register 3:	PWM Output Enable (PWMENABLE), offset 0x008	
Register 4:	PWM Output Inversion (PWMINVERT), offset 0x00C	1254
Register 5:	PWM Output Fault (PWMFAULT), offset 0x010	
Register 6:	PWM Interrupt Enable (PWMINTEN), offset 0x014	
Register 7:	PWM Raw Interrupt Status (PWMRIS), offset 0x018	
Register 8:	PWM Interrupt Status and Clear (PWMISC), offset 0x01C	1263

Register 9:	PWM Status (PWMSTATUS), offset 0x020	1266
Register 10:	PWM Fault Condition Value (PWMFAULTVAL), offset 0x024	1268
Register 11:	PWM Enable Update (PWMENUPD), offset 0x028	1270
Register 12:	PWM0 Control (PWM0CTL), offset 0x040	1274
Register 13:	PWM1 Control (PWM1CTL), offset 0x080	1274
Register 14:	PWM2 Control (PWM2CTL), offset 0x0C0	
Register 15:	PWM3 Control (PWM3CTL), offset 0x100	1274
Register 16:	PWM0 Interrupt and Trigger Enable (PWM0INTEN), offset 0x044	1279
Register 17:	PWM1 Interrupt and Trigger Enable (PWM1INTEN), offset 0x084	1279
Register 18:	PWM2 Interrupt and Trigger Enable (PWM2INTEN), offset 0x0C4	1279
Register 19:	PWM3 Interrupt and Trigger Enable (PWM3INTEN), offset 0x104	1279
Register 20:	PWM0 Raw Interrupt Status (PWM0RIS), offset 0x048	1282
Register 21:	PWM1 Raw Interrupt Status (PWM1RIS), offset 0x088	1282
Register 22:	PWM2 Raw Interrupt Status (PWM2RIS), offset 0x0C8	1282
Register 23:	PWM3 Raw Interrupt Status (PWM3RIS), offset 0x108	1282
Register 24:	PWM0 Interrupt Status and Clear (PWM0ISC), offset 0x04C	1284
Register 25:	PWM1 Interrupt Status and Clear (PWM1ISC), offset 0x08C	1284
Register 26:	PWM2 Interrupt Status and Clear (PWM2ISC), offset 0x0CC	1284
Register 27:	PWM3 Interrupt Status and Clear (PWM3ISC), offset 0x10C	1284
Register 28:	PWM0 Load (PWM0LOAD), offset 0x050	1286
Register 29:	PWM1 Load (PWM1LOAD), offset 0x090	1286
Register 30:	PWM2 Load (PWM2LOAD), offset 0x0D0	
Register 31:	PWM3 Load (PWM3LOAD), offset 0x110	1286
Register 32:	PWM0 Counter (PWM0COUNT), offset 0x054	1287
Register 33:	PWM1 Counter (PWM1COUNT), offset 0x094	1287
Register 34:	PWM2 Counter (PWM2COUNT), offset 0x0D4	1287
Register 35:	PWM3 Counter (PWM3COUNT), offset 0x114	1287
Register 36:	PWM0 Compare A (PWM0CMPA), offset 0x058	1288
Register 37:	PWM1 Compare A (PWM1CMPA), offset 0x098	1288
Register 38:	PWM2 Compare A (PWM2CMPA), offset 0x0D8	1288
Register 39:	PWM3 Compare A (PWM3CMPA), offset 0x118	1288
Register 40:	PWM0 Compare B (PWM0CMPB), offset 0x05C	1289
Register 41:	PWM1 Compare B (PWM1CMPB), offset 0x09C	1289
Register 42:	PWM2 Compare B (PWM2CMPB), offset 0x0DC	1289
Register 43:	PWM3 Compare B (PWM3CMPB), offset 0x11C	1289
Register 44:	PWM0 Generator A Control (PWM0GENA), offset 0x060	1290
Register 45:	PWM1 Generator A Control (PWM1GENA), offset 0x0A0	1290
Register 46:	PWM2 Generator A Control (PWM2GENA), offset 0x0E0	1290
Register 47:	PWM3 Generator A Control (PWM3GENA), offset 0x120	1290
Register 48:	PWM0 Generator B Control (PWM0GENB), offset 0x064	1293
Register 49:	PWM1 Generator B Control (PWM1GENB), offset 0x0A4	1293
Register 50:	PWM2 Generator B Control (PWM2GENB), offset 0x0E4	1293
Register 51:	PWM3 Generator B Control (PWM3GENB), offset 0x124	
Register 52:	PWM0 Dead-Band Control (PWM0DBCTL), offset 0x068	1296
Register 53:	PWM1 Dead-Band Control (PWM1DBCTL), offset 0x0A8	1296
Register 54:	PWM2 Dead-Band Control (PWM2DBCTL), offset 0x0E8	1296
Register 55:	PWM3 Dead-Band Control (PWM3DBCTL), offset 0x128	1296
Register 56:	PWM0 Dead-Band Rising-Edge Delay (PWM0DBRISE), offset 0x06C	1297

Register 57:	PWM1 Dead-Band Rising-Edge Delay (PWM1DBRISE), offset 0x0AC	1297
Register 58:	PWM2 Dead-Band Rising-Edge Delay (PWM2DBRISE), offset 0x0EC	1297
Register 59:	PWM3 Dead-Band Rising-Edge Delay (PWM3DBRISE), offset 0x12C	1297
Register 60:	PWM0 Dead-Band Falling-Edge-Delay (PWM0DBFALL), offset 0x070	1298
Register 61:	PWM1 Dead-Band Falling-Edge-Delay (PWM1DBFALL), offset 0x0B0	1298
Register 62:	PWM2 Dead-Band Falling-Edge-Delay (PWM2DBFALL), offset 0x0F0	1298
Register 63:	PWM3 Dead-Band Falling-Edge-Delay (PWM3DBFALL), offset 0x130	1298
Register 64:	PWM0 Fault Source 0 (PWM0FLTSRC0), offset 0x074	1299
Register 65:	PWM1 Fault Source 0 (PWM1FLTSRC0), offset 0x0B4	1299
Register 66:	PWM2 Fault Source 0 (PWM2FLTSRC0), offset 0x0F4	
Register 67:	PWM3 Fault Source 0 (PWM3FLTSRC0), offset 0x134	1299
Register 68:	PWM0 Fault Source 1 (PWM0FLTSRC1), offset 0x078	1301
Register 69:	PWM1 Fault Source 1 (PWM1FLTSRC1), offset 0x0B8	1301
Register 70:	PWM2 Fault Source 1 (PWM2FLTSRC1), offset 0x0F8	1301
Register 71:	PWM3 Fault Source 1 (PWM3FLTSRC1), offset 0x138	1301
Register 72:	PWM0 Minimum Fault Period (PWM0MINFLTPER), offset 0x07C	
Register 73:	PWM1 Minimum Fault Period (PWM1MINFLTPER), offset 0x0BC	
Register 74:	PWM2 Minimum Fault Period (PWM2MINFLTPER), offset 0x0FC	1304
Register 75:	PWM3 Minimum Fault Period (PWM3MINFLTPER), offset 0x13C	1304
Register 76:	PWM0 Fault Pin Logic Sense (PWM0FLTSEN), offset 0x800	1305
Register 77:	PWM1 Fault Pin Logic Sense (PWM1FLTSEN), offset 0x880	1305
Register 78:	PWM2 Fault Pin Logic Sense (PWM2FLTSEN), offset 0x900	1305
Register 79:	PWM3 Fault Pin Logic Sense (PWM3FLTSEN), offset 0x980	
Register 80:	PWM0 Fault Status 0 (PWM0FLTSTAT0), offset 0x804	1306
Register 81:	PWM1 Fault Status 0 (PWM1FLTSTAT0), offset 0x884	1306
Register 82:	PWM2 Fault Status 0 (PWM2FLTSTAT0), offset 0x904	
Register 83:	PWM3 Fault Status 0 (PWM3FLTSTAT0), offset 0x984	
Register 84:	PWM0 Fault Status 1 (PWM0FLTSTAT1), offset 0x808	
Register 85:	PWM1 Fault Status 1 (PWM1FLTSTAT1), offset 0x888	
Register 86:	PWM2 Fault Status 1 (PWM2FLTSTAT1), offset 0x908	
Register 87:	PWM3 Fault Status 1 (PWM3FLTSTAT1), offset 0x988	
Register 88:	PWM Peripheral Properties (PWMPP), offset 0xFC0	1311
Quadrature	Encoder Interface (QEI)	1313
Register 1:	QEI Control (QEICTL), offset 0x000	1319
Register 2:	QEI Status (QEISTAT), offset 0x004	1322
Register 3:	QEI Position (QEIPOS), offset 0x008	1323
Register 4:	QEI Maximum Position (QEIMAXPOS), offset 0x00C	1324
Register 5:	QEI Timer Load (QEILOAD), offset 0x010	
Register 6:	QEI Timer (QEITIME), offset 0x014	
Register 7:	QEI Velocity Counter (QEICOUNT), offset 0x018	1327
Register 8:	QEI Velocity (QEISPEED), offset 0x01C	1328
Register 9:	QEI Interrupt Enable (QEIINTEN), offset 0x020	1329
Register 10:	QEI Raw Interrupt Status (QEIRIS), offset 0x024	1331
Register 11:	OFI Interrupt Status and Clear (OFIISC), offset 0x028	1333

Revision History

The revision history table notes changes made between the indicated revisions of the LM4F232H5QC data sheet.

Table 1. Revision History

Date	Revision	Description
February 2013	14259.	■ In the System Control chapter:
		 Added note that when transitioning the system clock configuration to use the MOSC as the fundamental clock source, the MOSCDIS bit must be set prior to reselecting the MOSC or an undefined system clock configuration can sporadically occur.
		 Corrected bits 11:10 in Masked Interrupt Status and Clear (MISC) register.
		■ In the GPIO chapter, clarified ICR register operation and interrupt status clearing based on whether the GPIO signal was configured as an edge- or level-detect interrupt.
		■ In the ADC chapter, clarified that the system clock must be at the same frequency or higher than the ADC clock, and that all ADC modules share the same clock source.
		■ In the UART chapter, removed information on UART LIN protocol support, including registers UARTLCTL, UARTLSS and UARTLTIM and bits UARTCTL[6], UARTIM[15:13], UARTRIS[15:13] UARTMIS[15:13], and UARTICR[15:13].
		■ In the SSI chapter, clarified that, in Freescale SPI mode, a condition can be created where an EO interrupt is generated for every byte transferred even if the FIFO is full.
		■ In the I ² C chapter, added information on I ² C glitch suppression, including register I2CMCR2 and bit I2CMCR [6].
		■ In the PWM chapter, removed the PWM Peripheral Configuration (PWMPC) register.
		■ In the QEI chapter, clarified that once the QEI module has been enabled by setting the ENABLE b in the QEICTL register, it cannot be disabled. The only way to clear the ENABLE bit is to reset the module using the Quadrature Encoder Interface Software Reset (SRQEI) register.
		■ Combined Operating Characteristics and Electrical Characteristics chapters.
		■ In the Electrical Characteristics chapter, made numerous clarifications, corrections and improvements
		 In the Temperature Characteristics table, changed temperature to Case operating temperature range.
		 Modified Thermal Characteristics table and added clarifying footnote.
		Updated ESD Absolute Maximum Ratings table.
		In Maximum Ratings table, added clarifying footnote.
		 Split Recommended DC Operating Conditions table into two tables (Recommended DC Operatin Conditions and Recommended GPIO Pad Operating Conditions), added new V_{DDCDS} parameter and changed values for existing I_{OH} parameter.
		Rewrote Power and Brown-Out section.
		 Rewrote Reset section.
		Updated PIOSC Clock Characteristics table.
		 In Hibernation Module Battery Characteristics table, added clarifying footnote.
		In EEPROM Characteristics table, added clarifying footnote.

Table 1. Revision History (continued)

Date	Revision	Description				
		In Input/Output Pin Characteristics section:				
		Added note to GPIO Module Characteristics subsection.				
		Added footnotes to Pad Voltage/Current Characteristics for Fail-Safe Pins table.				
		Added footnotes to Non-Fail-Safe I/O Pad Voltage/Current Characteristics table.				
		 In ADC Electrical Characteristics table, corrected DNL parameter value and added Dynamic Characteristics section. 				
		 In SSI characteristics table, added values for slave mode, corrected T_{DMD}, T_{DMS}, and T_{DMH} parameter values, and added T_{DSS} and T_{DSH} values. 				
		Additional minor data sheet clarifications and corrections.				
January 2013	14259.	■ In System Control Chapter:				
		Enhanced Brown-Out Reset (BOR) capability:				
		 Clarified "Brown-Out Reset (BOR)" on page 220 to include new BOR trip point. A BOR0 and BOR1 trip point now exists. 				
		Added BOR1 bit to the Brown-Out Reset Control (PBORCTL) register.				
		Added VDDARIS and BORORIS bits to the Raw Interrupt Status (RIS) register. Also renamed bit 1 to BOR1RIS.				
		Added VDDAIM and BOR0IM bits to the Interrupt Mask Control (IMC) register. Also renamed bit 1 to BOR1IM.				
		 Added VDDAMIS and BOROMIS bits to the Masked Interrupt Status and Clear (MISC) register. Also renamed bit 1 to BORIMIS. 				
		 Clarified that the BOR bit in the Reset Cause (RESC) register applies to a BOR0 or BOR1 event. 				
		Corrected Power Architecture figure.				
		 Renamed Internal 30-kHz Oscillator to Low-Frequency Internal Oscillator (LFIOSC) as the frequency can have wide variations; refer to "Low-Frequency Internal Oscillator (LFIOSC) Specifications" on page 1392. 				
		 Removed the IOSCDIS bit in the Run-Mode Clock Configuration (RCC) register as it has no effect. 				
		Corrected register type for Peripheral Ready (PRx) registers to read-only.				
		■ Clarified "Waking from Hibernate" on page 500.				
		■ In Internal Memory chapter:				
		 Clarified Flash memory protection by adding content to "Flash Memory" on page 526 and correcting procedures in "Flash Memory Programming" on page 528. 				
		Added information on Debug Mass Erase to EEPROM section.				
		Added KEY bit to Boot Configuration (BOOTCFG) register.				
		■ Corrected reset for DMA Channel Wait-on-Request Status (DMAWAITSTAT) register.				
		■ Indicated that (in addition to PB0 and PB1), PJ0 and PJ1 are <i>not</i> 5-V tolerant when configured as GPIO inputs; they are limited to 3.6 V.				

Table 1. Revision History (continued)

Date	Revision	Description
		■ Noted that the upper 16 bits of the GPTM Timer A Value (GPTMTAV) and GPTM Timer B Value (GPTMTBV) registers are not used when in 16-bit mode.
		■ In the ADC chapter:
		Clarified ADC Module Clocking.
		Added BUSY bit (Busy Status) to ADC Active Sample Sequencer (ADCACTSS) register.
		 Added DITHER bit (Dither Enable) to ADC Control (ADCCTL) register.
		■ In the UART chapter:
		Clarified Serial IR (SIR) description.
		 Corrected reset value for the UART Raw Interrupt Status (UARTRIS) register.
		■ Corrected bit field length for CS bit in SSI Clock Configuration (SSICC) register.
		 Clarified that the termination resistors for the USB PHY have been added internally, and thus there is no need for external resistors.
		■ Corrected reset of PWM Peripheral Configuration (PWMPC) register.
		■ Updated QEI block diagram.
		■ In Operating Characteristics chapter, added case operating temperature range and updated Thermal Characteristics table.
		■ In Electrical Characteristics chapter:
		$-$ In Table 24-5 on page 1378, corrected V_{DD} min value and V_{IH} max value.
		 In Table 24-10 on page 1383, marked values as pending characterization.
		 In Table 24-13 on page 1391, clarified PLL frequency footnote.
		 In Table 24-16 on page 1392, corrected F_{LFIOSC} nom value.
		 In Table 24-17 on page 1392, added F_{HIBLFOSC} parameter and clarified T_{START} footnote.
		 Added information on crystal parameters to "Main Oscillator Specifications" on page 1393.
		 In Table 24-28 on page 1400, corrected I_{LKG+} parameter descriptions.
		 Added section "Types of I/O Pins and ESD Protection" on page 1400.
		 In Table 24-31 on page 1403, clarified that reference is to junction temperature. Also corrected DNL max value.
		 In Table 24-32 on page 1407, corrected parameter values.
		 In Table 24-34 on page 1411, clarified footnotes and corrected V_{OS} max value.
		Additional minor data sheet clarifications and corrections.
August 2012	14259.	■ In SysCtl chapter:
		Corrected reset for XTAL bit in RCC register.
		Removed module power control (PCx) registers.

Table 1. Revision History (continued)

Date	Revision	Description
		 Added a note to the Deep Sleep Clock Configuration (DSLPCLKCFG) register that to use the MOSC as the Deep-Sleep mode clock source, the MOSC must also be configured as the Run mode clock source.
		■ In Hibernation chapter:
		Added information on RTC Seconds/Subseconds mode to Functional Description.
		- Deleted bit 18 OSCHYS (32.768-kHz Oscillator Hysteresis Control) from Hibernation Control (HIBCTL) register.
		■ In μDMA chapter, corrected ADC μDMA Channel Assignments and clarified that the μDMA controller can only respond to burst requests by the ADC module.
		■ In GPIO chapter, added procedure to "Initialization and Configuration" section on how to configure the GPIO pins of a particular port.
		■ In General-Purpose Timer chapter, added information on Timer Compare Action Mode.
		■ In ADC chapter:
		– Clarified ADC and μDMA operation.
		Corrected reset for ADC Control (ADCCTL) register.
		■ In SSI chapter, added note to SSICR1 register that the EOT bit cannot be set to '1' when using uDMA.
		■ In I2C chapter:
		 Added note that both SDA and SCL signals must be connected to a positive supply voltage using a pullup resistor.
		Added section on repeated start sequence.
		Clarified "Clock Low Timeout" section.
		Added procedure to configure High Speed mode to "Initialization and Configuration" section.
		■ In USB chapter, added note that when the USB module is in operation, the system clock must be at least 20 MHz.
		■ In Electrical Characteristics chapter:
		 In Flash Memory Characteristics and EEPROM Characteristics tables, corrected data retention parameter values.
		Additional minor data sheet clarifications and corrections.
April 2012	12454.2480	Document revision number is now auto-generated and indicates the revision of the source files.
		■ In the JTAG chapter, clarified that the "Recovering a Locked Microcontroller" procedure erases EEPROM and returns its wear-leveling counters to factory default values.
		■ In the Hibernation Module chapter, corrected the reset value of the Hibernation RTC Sub Seconds (HIBRTCSS) register.
		■ In the System Control chapter, reorganized registers to group legacy registers at the end of the chapter.
		■ In the uDMA chapter, in the "µDMA Channel Assignments" and "Request Type Support" tables, corrected to show uDMA support for burst requests from the general-purpose timer, not single requests.

Table 1. Revision History (continued)

Date	Revision	Description
		■ In the SSI chapter, added the SLBY6 bit to the SSI Control 1 (SSICR1) register. This allows the system clock to operate at least 6 times faster (overriding 12 times faster normally) than SSICLK.
		■ In the I ² C chapter, clarified description of Quick Command.
		In the Operating Characteristics chapter, deleted the Maximum power dissipation parameter from the "Thermal Characteristics" table.
		■ In the Electrical Characteristics chapter:
		Removed pending characterization notes in a number of tables where data has been reviewed.
		 In the Power Characteristics table, adjusted the minimum, nominal, and maximum values for POR and BOR thresholds.
		 In the Main Oscillator Input Characteristics table, adjusted the maximum value for the main oscillator startup time.
		 In the HIB Oscillator Input Characteristics table, added Max value for Oscillator startup time and changed Min and Max values for External clock reference duty cycle.
		Added Crystal Parameters table.
		 In the Hibernation Module Battery Characteristics table, adjusted the values for low battery detect voltage.
		 In the Flash Memory Characteristics table, adjusted the maximum values for T_{PROG64} and T_{ERASE}.
		 In the GPIO Module Characteristics table, adjusted the values for the GPIO rise and fall times.
		 In the ADC Electrical Characteristics table, updated Max value for the ADC input common mode voltage parameter, and adjusted system performance parameter values.
		 In the SSI Characteristics table, adjusted values for SSICIk rise and fall times.
		In Preliminary Current Consumption table, updated Nom value for Deep-sleep mode parameter.
		Additional minor data sheet clarifications and corrections.
March 2012	12013	■ In Cortex-M4 Peripherals chapter:
		 Corrected missing bits in Interrupt 128-138 Set Enable (EN4), Interrupt 128-138 Clear Enable (DIS4), Interrupt 128-138 Set Pending (PEND4), Interrupt 128-138 Clear Pending (UNPEND4), and Interrupt 128-138 Active Bit (ACTIVE4) registers.
		 Added missing Interrupt 132-135 Priority (PRI33) and Interrupt 136-138 Priority (PRI34) registers.
		■ In the System Control chapter,
		Corrected Power Architecture figure.
		 Added note that the configuration of the system clock must not be changed while an EEPROM operation is in process.
		 Corrected to 1 the reset for bit 27 in the Device Identification 0 (DID0) register.
		 Clarified the Software Reset (SRx), Run Mode Clock Gating Control (RCGCx), Sleep Mode Clock Gating Control (SCGCx), Deep-Sleep Mode Clock Gating Control (DCGCx), Power Control (PCx) and Peripheral Ready (PRx) registers by removing those bits without meaning because that feature is not present. Conversely, the Peripheral Present (PPx) registers show bit fields available for all devices in this family, with a 0 indicating the feature is not present.

Table 1. Revision History (continued)

Date	Revision	De	scription
		-	In the Hibernation chapter:
			Corrected Hibernation Module block diagram.
			Clarified the implementation for VDD3ON mode.
			 Removed LOWBATEN bit from the Hibernation Control (HIBCTL) register.
		-	In the Timer chapter, noted that if PWM output inversion is enabled, edge detection interrupt behavior is reversed.
		-	In the Watchdog Timers chapter, added information on servicing the watchdog timer to the Initialization and Configuration section.
		-	In the ADC chapter:
			Corrected figure "ADC Input Equivalency Diagram".
			 Changed the voltage reference internal signal names to VREFP and VREFN.
			Clarified "Differential Sampling" section.
			Corrected figure "Internal Temperature Sensor Characteristic".
			 Corrected PSn bit field locations in ADC Trigger Source Select (ADCTSSEL) register.
			 Corrected resets for ADC Control (ADCCTL) and ADC Sample Sequence Control 3 (ADCSCTL3) registers.
		-	In the UART chapter:
			 Added note to UART LIN Timer (UARTLTIM) register that if the PIOSC is being used as the UART baud clock, the value in this register should be read twice to ensure the data is correct.
			- Removed RANGE bit from the UART 9-Bit Self Address Mask (UART9BITAMASK) register.
			Corrected CS bit field values in the UART Clock Configuration (UARTCC) register.
		•	In the SSI chapter:
			Clarified the steps in the initialization and configuration section.
			 Corrected CS bit field values in the SSI Clock Configuration (SSICC) register.
		-	In the I ² C chapter:
			Clarified the operation of the clock low timeout.
			 Added information about high-speed operation and Fast Plus mode.
			 Corrected reset for I²C Master Bus Monitor (I2CMBMON) register.
		-	In the USB chapter, corrected reset for ECNT bit in USB Peripheral Properties (USBPP) register.
		•	In the Analog Comparators chapter:
			Rewrote Internal Reference Programming section.
			 Corrected bit description for RNG in the Analog Comparator Reference Voltage Control (ACREFCTL) register.
		-	In the Signal Tables chapter, deleted erroneously included LPC signals.
		-	In the Electrical Characteristics chapter:

Table 1. Revision History (continued)

Date	Revision	Description
		 Clarified GPIO pad operation and specifications, including ESD protection, V_{OH}, V_{OL}, input hysteresis, input leakage, and injection current.
		Corrected Nom value for TCK clock Low and High time.
		Clarified reset timing when in Deep-sleep mode.
		Corrected frequency range for the internal 30-kHz oscillator.
		$-$ Clarified V_{IH} , V_{IL} , and input hysteresis for the Hibernation oscillator inputs.
		Corrected minimum system clock frequency when using the USB module.
		 Changed unit values for T_{WAKE_TO_HIB} from microseconds to hibernate clocks in table "Hibernation Module AC Characteristics".
		Added values to the table "GPIO Module Characteristics".
		Added specifications for the ADC when using the internal reference.
		Added specification for ADC input common mode voltage when in differential mode.
		Added specification for current consumption on VDDA.
		■ Additional minor data sheet clarifications and corrections.
November 2011	11003	■ Re-organized Architectural Overview chapter.
		 In the System Control chapter: Corrected reset value for Run Mode Clock Gating Control Register 0 (RCGC0) register. Corrected reset for the System Properties (SYSPROP) register. Removed ™PSW bit from Non-Volatile Memory Information (NVMSTAT) register as the ROM Software Map (ROMSWMAP) register contains this information.
		■ Changed bit names in System Exception Raw Interrupt Status (SYSEXCRIS), System Exception Interrupt Mask (SYSEXCIM), System Exception Masked Interrupt Status (SYSEXCMIS), and System Exception Interrupt Clear (SYSEXCIC) registers to indicate they are for floating-point exceptions.
		■ In Hibernation chapter, added section "Arbitrary Power Removal" and corrected figure "Using a Dedicated Oscillator as the Hibernation Clock Source with VDD3ON Mode ".
		In the Internal Memory chapter, clarified programming and use of the non-volatile registers, including corrections to the Boot Configuration (BOOTCFG) and User Register n (USER_REGn) registers.
		■ In the GPIO chapter, corrected table "GPIO Pins With Non-Zero Reset Values".
		■ In the General-Purpose Timers chapter, added clarifications on timer operation.
		■ In the UART chapter, clarified interrupt behavior.
		■ In the I ² C chapter: - Added content for Fast-Mode Plus (1 Mbps) mode and High-Speed mode (3.33 Mbps), correcting the reset value of the Device Capabilities 2 (DC2), I ² C Master Control/Status (I2CMCS), and I ² C Peripheral Properties (I2CPP) registers. - Corrected reset for the I ² C Master Control/Status (I2CMCS) register. - Added the HSTPR bit to the I ² C Master Timer Period (I2CMTPR) register. - Added the I ² C Peripheral Configuration (I2CPC) register.
		■ In the USB chapter:
		Corrected description for the USB Device RESUME Interrupt Mask (USBDRIM) register.

Table 1. Revision History (continued)

Date	Revision	Description
		■ In the Analog Comparators chapter:
		Corrected table "Internal Reference Voltage and ACREFCTL Field Values".
		Corrected bit fields in the Analog Comparator Peripheral Properties (ACMPPP) register.
		 In the Electrical Characteristics chapter: Clarified load capacitance equations.
		Corrected values in table "Analog Comparator Voltage Reference Characteristics".
		Additional minor data sheet clarifications and corrections.
September 2011	10502	Started tracking revision history.

About This Document

This data sheet provides reference information for the LM4F232H5QC microcontroller, describing the functional blocks of the system-on-chip (SoC) device designed around the ARM® Cortex™-M4F core.

Audience

This manual is intended for system software developers, hardware designers, and application developers.

About This Manual

This document is organized into sections that correspond to each major feature.

Related Documents

The following related documents are available on the Stellaris® web site at www.ti.com/stellaris:

- Stellaris® Errata
- ARM® Cortex™-M4 Errata
- Cortex™-M3/M4 Instruction Set Technical User's Manual
- Stellaris® Boot Loader User's Guide
- Stellaris® Graphics Library User's Guide
- Stellaris® Peripheral Driver Library User's Guide
- Stellaris® ROM User's Guide
- Stellaris® USB Library User's Guide

The following related documents are also referenced:

- ARM® Debug Interface V5 Architecture Specification
- ARM® Embedded Trace Macrocell Architecture Specification
- IEEE Standard 1149.1-Test Access Port and Boundary-Scan Architecture

This documentation list was current as of publication date. Please check the web site for additional documentation, including application notes and white papers.

Documentation Conventions

This document uses the conventions shown in Table 2 on page 47.

Table 2. Documentation Conventions

Notation	Meaning				
General Register Notation					
REGISTER	APB registers are indicated in uppercase bold. For example, PBORCTL is the Power-On and Brown-Out Reset Control register. If a register name contains a lowercase n, it represents more than one register. For example, SRCRn represents any (or all) of the three Software Reset Control registers: SRCR0 , SRCR1 , and SRCR2 .				
bit	A single bit in a register.				
bit field	Two or more consecutive and related bits.				
offset 0xnnn	A hexadecimal increment to a register's address, relative to that module's base address as specified in Table 2-4 on page 96.				
Register N	Registers are numbered consecutively throughout the document to aid in referencing them. The register number has no meaning to software.				
reserved	Register bits marked <i>reserved</i> are reserved for future use. In most cases, reserved bits are set to 0; however, user software should not rely on the value of a reserved bit. To provide software compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.				
yy:xx	The range of register bits inclusive from xx to yy. For example, 31:15 means bits 15 through 31 in that register.				
Register Bit/Field Types	This value in the register bit diagram indicates whether software running on the controller can change the value of the bit field.				
RC	Software can read this field. The bit or field is cleared by hardware after reading the bit/field.				
RO	Software can read this field. Always write the chip reset value.				
R/W	Software can read or write this field.				
R/WC	Software can read or write this field. Writing to it with any value clears the register.				
R/W1C	Software can read or write this field. A write of a 0 to a W1C bit does not affect the bit value in the register. A write of a 1 clears the value of the bit in the register; the remaining bits remain unchanged.				
	This register type is primarily used for clearing interrupt status bits where the read operation provides the interrupt status and the write of the read value clears only the interrupts being reported at the time the register was read.				
R/W1S	Software can read or write a 1 to this field. A write of a 0 to a R/W1S bit does not affect the bit value in the register.				
W1C	Software can write this field. A write of a 0 to a W1C bit does not affect the bit value in the register. A write of a 1 clears the value of the bit in the register; the remaining bits remain unchanged. A read of the register returns no meaningful data.				
	This register is typically used to clear the corresponding bit in an interrupt register.				
WO	Only a write by software is valid; a read of the register returns no meaningful data.				
Register Bit/Field Reset Value	This value in the register bit diagram shows the bit/field value after any reset, unless noted.				
0	Bit cleared to 0 on chip reset.				
1	Bit set to 1 on chip reset.				
-	Nondeterministic.				
Pin/Signal Notation					
[]	Pin alternate function; a pin defaults to the signal without the brackets.				
pin	Refers to the physical connection on the package.				
signal	Refers to the electrical signal encoding of a pin.				

Table 2. Documentation Conventions (continued)

Notation	Meaning		
assert a signal	Change the value of the signal from the logically False state to the logically True state. For active High signals, the asserted signal value is 1 (High); for active Low signals, the asserted signal value is 0 (Low). The active polarity (High or Low) is defined by the signal name (see SIGNAL and SIGNAL below).		
deassert a signal	Change the value of the signal from the logically True state to the logically False state.		
SIGNAL	Signal names are in uppercase and in the Courier font. An overbar on a signal name indicates that it is active Low. To assert SIGNAL is to drive it Low; to deassert SIGNAL is to drive it High.		
SIGNAL	Signal names are in uppercase and in the Courier font. An active High signal has no overbar. To assert SIGNAL is to drive it High; to deassert SIGNAL is to drive it Low.		
Numbers			
Х	An uppercase X indicates any of several values is allowed, where X can be any legal pattern. For example, a binary value of 0X00 can be either 0100 or 0000, a hex value of 0xX is 0x0 or 0x1, and so on.		
0x	Hexadecimal numbers have a prefix of 0x. For example, 0x00FF is the hexadecimal number FF.		
	All other numbers within register tables are assumed to be binary. Within conceptual information, binary numbers are indicated with a b suffix, for example, 1011b, and decimal numbers are written without a prefix or suffix.		

1 Architectural Overview

Texas Instrument's Stellaris[®] family of microcontrollers provide designers a high-performance ARM[®] Cortex[™]-M-based architecture with a broad set of integration capabilities and a strong ecosystem of software and development tools. Targeting performance and flexibility, the Stellaris architecture offers a 80 MHz Cortex-M with FPU, a variety of integrated memories and multiple programmable GPIO. Stellaris devices offer consumers compelling cost-effective solutions by integrating application-specific peripherals and providing a comprehensive library of software tools which minimize board costs and design-cycle time. Offering quicker time-to-market and cost savings, the Stellaris family of microcontrollers is the leading choice in high-performance 32-bit applications.

This chapter contains an overview of the Stellaris LM4F series of microcontrollers as well as details on the LM4F232H5QC microcontroller:

- "Series Overview" on page 49
- "LM4F232H5QC Microcontroller Overview" on page 50
- "LM4F232H5QC Microcontroller Features" on page 53
- "LM4F232H5QC Microcontroller Hardware Details" on page 72

1.1 Series Overview

The Stellaris LM4F series of ARM Cortex-M4 microcontrollers provides top performance and advanced integration. The product family is positioned for cost-conscious applications requiring significant control processing and connectivity capabilities such as:

- Low power, hand-held smart devices
- Gaming equipment
- Home and commercial site monitoring and control
- Motion control
- Medical instrumentation
- Test and measurement equipment
- Factory automation
- Fire and security
- Smart Energy/Smart Grid solutions
- Intelligent lighting control
- Transportation

For applications requiring extreme conservation of power, the LM4F232H5QC microcontroller features a battery-backed Hibernation module to efficiently power down the LM4F232H5QC to a low-power state during extended periods of inactivity. With a power-up/power-down sequencer, a continuous time counter (RTC), multiple wake-from-hibernate options, a high-speed interface to the system bus, and dedicated battery-backed memory, the Hibernation module positions the LM4F232H5QC microcontroller perfectly for battery applications.

In addition, the LM4F232H5QC microcontroller offers the advantages of ARM's widely available development tools, System-on-Chip (SoC) infrastructure IP applications, and a large user community. Additionally, the microcontroller uses ARM's Thumb®-compatible Thumb-2 instruction set to reduce memory requirements and, thereby, cost. Finally, the LM4F232H5QC microcontroller is code-compatible to all members of the extensive Stellaris family; providing flexibility to fit precise needs.

Texas Instruments offers a complete solution to get to market quickly, with evaluation and development boards, white papers and application notes, an easy-to-use peripheral driver library, and a strong support, sales, and distributor network.

Stellaris® LM4F Series MCU 256 KB Analog ARM® Flash LDO Voltage Regulator Cortex™-M4F 32 KB 80 MHz 3 Analog Comparators SRAM JTAG MPU ROM NVIC ETM 2KB EEPROM SWD/T **Temp Sensor** Serial Interfaces **Motion Control** System 8 UARTs 2 Quadrature Encoder Inputs Clocks, Reset System Control 4 SSI/SPI SysTick Timer 16 PWM Outputs USB Full Speed Host / Device / OTG 12 Timer/PWM/CCP 6 each 32-bit or 2x16-bit 6 each 64-bit or 2x32-bit 2CAN 2 Watchdog Timers 6 |2C **GPIOs** 32ch DMA Precision Oscillator Battery-Backed Hibernate

Figure 1-1. Stellaris® Blizzard-class Block Diagram

The Stellaris LM4F microcontrollers consist of fifteen pin-compatible series of devices, summarized below. Each series has a range of embedded Flash and SRAM sizes.

Table 1-1. Stellaris LM4F Device Series

General MCU (LM4F11x Series)	General MCU + USB Device (LM4F12x Series)	General MCU + USB OTG (LM4F13x Series)	Motion Control (LM4F21x Series)	Motion Control + USB OTG (LM4F23x Series)	Package
LM4F110	LM4F120	LM4F130	LM4F210	LM4F230	64-pin LQFP
LM4F111	LM4F121	LM4F131	LM4F211	LM4F231	64-pin LQFP
LM4F112	LM4F122	LM4F132	LM4F212	LM4F232	100-pin LQFP
					144-pin LQFP
					157-ball BGA (LM4F212 and LM4F232 only)

1.2 LM4F232H5QC Microcontroller Overview

The LM4F232H5QC microcontroller combines complex integration and high performance with the features shown in Table 1-2.

Table 1-2. LM4F232H5QC Microcontroller Features

Feature	Description
Core	ARM Cortex-M4F processor core
Performance	80-MHz operation; 100 DMIPS performance
Flash	256 KB single-cycle Flash memory
System SRAM	32 KB single-cycle SRAM
EEPROM	2KB of EEPROM
Internal ROM	Internal ROM loaded with StellarisWare® software
Communication Interfaces	
Universal Asynchronous Receivers/Transmitter (UART)	Eight UARTs
Synchronous Serial Interface (SSI)	Four SSI modules
Inter-Integrated Circuit (I ² C)	Six I ² C modules with four transmission speeds including high-speed mode
Controller Area Network (CAN)	Two CAN 2.0 A/B controllers
Universal Serial Bus (USB)	USB 2.0 OTG/Host/Device
System Integration	
Micro Direct Memory Access (µDMA)	ARM® PrimeCell® 32-channel configurable µDMA controller
General-Purpose Timer (GPTM)	Six 16/32-bit GPTM blocks and six 32/64-bit Wide GPTM blocks
Watchdog Timer (WDT)	Two watchdog timers
Hibernation Module (HIB)	Low-power battery-backed Hibernation module
General-Purpose Input/Output (GPIO)	10 physical GPIO blocks
Advanced Motion Control	
Pulse Width Modulator (PWM)	Two PWM modules, each with four PWM generator blocks and a control block, for a total of 16 PWM outputs.
Quadrature Encoder Interface (QEI)	Two QEI modules
Analog Support	
Analog-to-Digital Converter (ADC)	Two 12-bit ADC modules with a maximum sample rate of one million samples/second
Analog Comparator Controller	Three independent integrated analog comparators
Digital Comparator	16 digital comparators
JTAG and Serial Wire Debug (SWD)	One JTAG module with integrated ARM SWD
Package	100-pin LQFP
Operating Range	Industrial (-40°C to 85°C) temperature range

Figure 1-2 on page 52 shows the features on the LM4F232H5QC microcontroller. Note that there are two on-chip buses that connect the core to the peripherals. The Advanced Peripheral Bus (APB) bus is the legacy bus. The Advanced High-Performance Bus (AHB) bus provides better back-to-back access performance than the APB bus.




Figure 1-2. Stellaris LM4F232H5QC Microcontroller High-Level Block Diagram

1.3 LM4F232H5QC Microcontroller Features

The LM4F232H5QC microcontroller component features and general function are discussed in more detail in the following section.

1.3.1 ARM Cortex-M4F Processor Core

All members of the Stellaris product family, including the LM4F232H5QC microcontroller, are designed around an ARM Cortex-M processor core. The ARM Cortex-M processor provides the core for a high-performance, low-cost platform that meets the needs of minimal memory implementation, reduced pin count, and low power consumption, while delivering outstanding computational performance and exceptional system response to interrupts.

1.3.1.1 Processor Core (see page 73)

- 32-bit ARM Cortex-M4F architecture optimized for small-footprint embedded applications
- 80-MHz operation; 100 DMIPS performance
- Outstanding processing performance combined with fast interrupt handling
- Thumb-2 mixed 16-/32-bit instruction set delivers the high performance expected of a 32-bit ARM core in a compact memory size usually associated with 8- and 16-bit devices, typically in the range of a few kilobytes of memory for microcontroller-class applications
 - Single-cycle multiply instruction and hardware divide
 - Atomic bit manipulation (bit-banding), delivering maximum memory utilization and streamlined peripheral control
 - Unaligned data access, enabling data to be efficiently packed into memory
- IEEE754-compliant single-precision Floating-Point Unit (FPU)
- 16-bit SIMD vector processing unit
- Fast code execution permits slower processor clock or increases sleep mode time
- Harvard architecture characterized by separate buses for instruction and data
- Efficient processor core, system and memories
- Hardware division and fast digital-signal-processing orientated multiply accumulate
- Saturating arithmetic for signal processing
- Deterministic, high-performance interrupt handling for time-critical applications
- Memory protection unit (MPU) to provide a privileged mode for protected operating system functionality
- Enhanced system debug with extensive breakpoint and trace capabilities
- Serial Wire Debug and Serial Wire Trace reduce the number of pins required for debugging and tracing

- Migration from the ARM7 processor family for better performance and power efficiency
- Optimized for single-cycle Flash memory usage up to specific frequencies; see "Internal Memory" on page 522 for more information.
- Ultra-low power consumption with integrated sleep modes

1.3.1.2 System Timer (SysTick) (see page 127)

ARM Cortex-M4F includes an integrated system timer, SysTick. SysTick provides a simple, 24-bit, clear-on-write, decrementing, wrap-on-zero counter with a flexible control mechanism. The counter can be used in several different ways, for example:

- An RTOS tick timer that fires at a programmable rate (for example, 100 Hz) and invokes a SysTick routine
- A high-speed alarm timer using the system clock
- A variable rate alarm or signal timer—the duration is range-dependent on the reference clock used and the dynamic range of the counter
- A simple counter used to measure time to completion and time used
- An internal clock-source control based on missing/meeting durations

1.3.1.3 Nested Vectored Interrupt Controller (NVIC) (see page 128)

The LM4F232H5QC controller includes the ARM Nested Vectored Interrupt Controller (NVIC). The NVIC and Cortex-M4F prioritize and handle all exceptions in Handler Mode. The processor state is automatically stored to the stack on an exception and automatically restored from the stack at the end of the Interrupt Service Routine (ISR). The interrupt vector is fetched in parallel to the state saving, enabling efficient interrupt entry. The processor supports tail-chaining, meaning that back-to-back interrupts can be performed without the overhead of state saving and restoration. Software can set eight priority levels on 7 exceptions (system handlers) and 85 interrupts.

- Deterministic, fast interrupt processing: always 12 cycles, or just 6 cycles with tail-chaining (these values reflect no FPU stacking)
- External non-maskable interrupt signal (NMI) available for immediate execution of NMI handler for safety critical applications
- Dynamically reprioritizable interrupts
- Exceptional interrupt handling via hardware implementation of required register manipulations

1.3.1.4 System Control Block (SCB) (see page 129)

The SCB provides system implementation information and system control, including configuration, control, and reporting of system exceptions.

1.3.1.5 Memory Protection Unit (MPU) (see page 129)

The MPU supports the standard ARM7 Protected Memory System Architecture (PMSA) model. The MPU provides full support for protection regions, overlapping protection regions, access permissions, and exporting memory attributes to the system.

1.3.1.6 Floating-Point Unit (FPU) (see page 134)

The FPU fully supports single-precision add, subtract, multiply, divide, multiply and accumulate, and square root operations. It also provides conversions between fixed-point and floating-point data formats, and floating-point constant instructions.

- 32-bit instructions for single-precision (C float) data-processing operations
- Combined multiply and accumulate instructions for increased precision (Fused MAC)
- Hardware support for conversion, addition, subtraction, multiplication with optional accumulate, division, and square-root
- Hardware support for denormals and all IEEE rounding modes
- 32 dedicated 32-bit single-precision registers, also addressable as 16 double-word registers
- Decoupled three stage pipeline

1.3.2 On-Chip Memory

The LM4F232H5QC microcontroller is integrated with the following set of on-chip memory and features:

- 32 KB single-cycle SRAM
- 256 KB Flash memory
- 2KB EEPROM
- Internal ROM loaded with StellarisWare software:
 - Stellaris Peripheral Driver Library
 - Stellaris Boot Loader
 - Advanced Encryption Standard (AES) cryptography tables
 - Cyclic Redundancy Check (CRC) error detection functionality

1.3.2.1 SRAM (see page 523)

The LM4F232H5QC microcontroller provides 32 KB of single-cycle on-chip SRAM. The internal SRAM of the Stellaris devices is located at offset 0x2000.0000 of the device memory map.

Because read-modify-write (RMW) operations are very time consuming, ARM has introduced *bit-banding* technology in the Cortex-M4F processor. With a bit-band-enabled processor, certain regions in the memory map (SRAM and peripheral space) can use address aliases to access individual bits in a single, atomic operation.

Data can be transferred to and from the SRAM using the Micro Direct Memory Access Controller (µDMA).

1.3.2.2 Flash Memory (see page 526)

The LM4F232H5QC microcontroller provides 256 KB of single-cycle on-chip Flash memory. The Flash memory is organized as a set of 1-KB blocks that can be individually erased. Erasing a block causes the entire contents of the block to be reset to all 1s. These blocks are paired into a set of 2-KB blocks that can be individually protected. The blocks can be marked as read-only or execute-only, providing different levels of code protection. Read-only blocks cannot be erased or programmed, protecting the contents of those blocks from being modified. Execute-only blocks

cannot be erased or programmed, and can only be read by the controller instruction fetch mechanism, protecting the contents of those blocks from being read by either the controller or by a debugger.

1.3.2.3 ROM (see page 524)

The LM4F232H5QC ROM is preprogrammed with the following software and programs:

- Stellaris Peripheral Driver Library
- Stellaris Boot Loader
- Advanced Encryption Standard (AES) cryptography tables
- Cyclic Redundancy Check (CRC) error-detection functionality

The Stellaris Peripheral Driver Library is a royalty-free software library for controlling on-chip peripherals with a boot-loader capability. The library performs both peripheral initialization and control functions, with a choice of polled or interrupt-driven peripheral support. In addition, the library is designed to take full advantage of the stellar interrupt performance of the ARM Cortex-M4F core. No special pragmas or custom assembly code prologue/epilogue functions are required. For applications that require in-field programmability, the royalty-free Stellaris Boot Loader can act as an application loader and support in-field firmware updates.

The Advanced Encryption Standard (AES) is a publicly defined encryption standard used by the U.S. Government. AES is a strong encryption method with reasonable performance and size. In addition, it is fast in both hardware and software, is fairly easy to implement, and requires little memory. The Texas Instruments encryption package is available with full source code, and is based on lesser general public license (LGPL) source. An LGPL means that the code can be used within an application without any copyleft implications for the application (the code does not automatically become open source). Modifications to the package source, however, must be open source.

CRC (Cyclic Redundancy Check) is a technique to validate a span of data has the same contents as when previously checked. This technique can be used to validate correct receipt of messages (nothing lost or modified in transit), to validate data after decompression, to validate that Flash memory contents have not been changed, and for other cases where the data needs to be validated. A CRC is preferred over a simple checksum (e.g. XOR all bits) because it catches changes more readily.

1.3.2.4 **EEPROM** (see page 531)

The LM4F232H5QC microcontroller includes an EEPROM with the following features:

- 2Kbytes of memory accessible as 512 32-bit words
- 32 blocks of 16 words (64 bytes) each
- Built-in wear leveling
- Access protection per block
- Lock protection option for the whole peripheral as well as per block using 32-bit to 96-bit unlock codes (application selectable)
- Interrupt support for write completion to avoid polling

■ Endurance of 500K writes (when writing at fixed offset in every alternate page in circular fashion) to 15M operations (when cycling through two pages) per each 2-page block.

1.3.3 Serial Communications Peripherals

The LM4F232H5QC controller supports both asynchronous and synchronous serial communications with:

- Two CAN 2.0 A/B controllers
- USB 2.0 OTG/Host/Device
- Eight UARTs with IrDA, 9-bit and ISO 7816 support.
 - UART1 (modem flow control and modem status)
- Six I²C modules with four transmission speeds including high-speed mode
- Four Synchronous Serial Interface modules (SSI)

The following sections provide more detail on each of these communications functions.

1.3.3.1 Controller Area Network (CAN) (see page 1053)

Controller Area Network (CAN) is a multicast shared serial-bus standard for connecting electronic control units (ECUs). CAN was specifically designed to be robust in electromagnetically noisy environments and can utilize a differential balanced line like RS-485 or twisted-pair wire. Originally created for automotive purposes, it is now used in many embedded control applications (for example, industrial or medical). Bit rates up to 1 Mbps are possible at network lengths below 40 meters. Decreased bit rates allow longer network distances (for example, 125 Kbps at 500m).

A transmitter sends a message to all CAN nodes (broadcasting). Each node decides on the basis of the identifier received whether it should process the message. The identifier also determines the priority that the message enjoys in competition for bus access. Each CAN message can transmit from 0 to 8 bytes of user information.

The LM4F232H5QC microcontroller includes two CAN units with the following features:

- CAN protocol version 2.0 part A/B
- Bit rates up to 1 Mbps
- 32 message objects with individual identifier masks
- Maskable interrupt
- Disable Automatic Retransmission mode for Time-Triggered CAN (TTCAN) applications
- Programmable loopback mode for self-test operation
- Programmable FIFO mode enables storage of multiple message objects
- Gluelessly attaches to an external CAN transceiver through the CANnTX and CANnRX signals

1.3.3.2 Universal Serial Bus (USB) (see page 1104)

Universal Serial Bus (USB) is a serial bus standard designed to allow peripherals to be connected and disconnected using a standardized interface without rebooting the system.

The LM4F232H5QC microcontroller supports three configurations in USB 2.0 full and low speed: USB Device, USB Host, and USB On-The-Go (negotiated on-the-go as host or device when connected to other USB-enabled systems).

The USB module has the following features:

- Complies with USB-IF (Implementer's Forum) certification standards
- USB 2.0 full-speed (12 Mbps) and low-speed (1.5 Mbps) operation with integrated PHY
- Link Power Management support which uses link-state awareness to reduce power usage
- 4 transfer types: Control, Interrupt, Bulk, and Isochronous
- 16 endpoints
 - 1 dedicated control IN endpoint and 1 dedicated control OUT endpoint
 - 7 configurable IN endpoints and 7 configurable OUT endpoints
- 4 KB dedicated endpoint memory: one endpoint may be defined for double-buffered 1023-byte isochronous packet size
- VBUS droop and valid ID detection and interrupt
- Efficient transfers using Micro Direct Memory Access Controller (μDMA)
 - Separate channels for transmit and receive for up to three IN endpoints and three OUT endpoints
 - Channel requests asserted when FIFO contains required amount of data

1.3.3.3 **UART** (see page 898)

A Universal Asynchronous Receiver/Transmitter (UART) is an integrated circuit used for RS-232C serial communications, containing a transmitter (parallel-to-serial converter) and a receiver (serial-to-parallel converter), each clocked separately.

The LM4F232H5QC microcontroller includes eight fully programmable 16C550-type UARTs. Although the functionality is similar to a 16C550 UART, this UART design is not register compatible. The UART can generate individually masked interrupts from the Rx, Tx, modem flow control, modem status, and error conditions. The module generates a single combined interrupt when any of the interrupts are asserted and are unmasked.

The eight UARTs have the following features:

- Programmable baud-rate generator allowing speeds up to 5 Mbps for regular speed (divide by 16) and 10 Mbps for high speed (divide by 8)
- Separate 16x8 transmit (TX) and receive (RX) FIFOs to reduce CPU interrupt service loading
- Programmable FIFO length, including 1-byte deep operation providing conventional double-buffered interface

- FIFO trigger levels of 1/8, 1/4, 1/2, 3/4, and 7/8
- Standard asynchronous communication bits for start, stop, and parity
- Line-break generation and detection
- Fully programmable serial interface characteristics
 - 5, 6, 7, or 8 data bits
 - Even, odd, stick, or no-parity bit generation/detection
 - 1 or 2 stop bit generation
- IrDA serial-IR (SIR) encoder/decoder providing
 - Programmable use of IrDA Serial Infrared (SIR) or UART input/output
 - Support of IrDA SIR encoder/decoder functions for data rates up to 115.2 Kbps half-duplex
 - Support of normal 3/16 and low-power (1.41-2.23 μs) bit durations
 - Programmable internal clock generator enabling division of reference clock by 1 to 256 for low-power mode bit duration
- Support for communication with ISO 7816 smart cards
- Modem flow control and status (on UART1)
- EIA-485 9-bit support
- Standard FIFO-level and End-of-Transmission interrupts
- Efficient transfers using Micro Direct Memory Access Controller (μDMA)
 - Separate channels for transmit and receive
 - Receive single request asserted when data is in the FIFO; burst request asserted at programmed FIFO level
 - Transmit single request asserted when there is space in the FIFO; burst request asserted at programmed FIFO level

1.3.3.4 I^2C (see page 1002)

The Inter-Integrated Circuit (I^2C) bus provides bi-directional data transfer through a two-wire design (a serial data line SDA and a serial clock line SCL). The I^2C bus interfaces to external I^2C devices such as serial memory (RAMs and ROMs), networking devices, LCDs, tone generators, and so on. The I^2C bus may also be used for system testing and diagnostic purposes in product development and manufacture.

Each device on the I²C bus can be designated as either a master or a slave. I²C module supports both sending and receiving data as either a master or a slave and can operate simultaneously as both a master and a slave. Both the I²C master and slave can generate interrupts.

The LM4F232H5QC microcontroller includes six I²C modules with the following features:

- Devices on the I²C bus can be designated as either a master or a slave
 - Supports both transmitting and receiving data as either a master or a slave
 - Supports simultaneous master and slave operation
- Four I²C modes
 - Master transmit
 - Master receive
 - Slave transmit
 - Slave receive
- Four transmission speeds:
 - Standard (100 Kbps)
 - Fast-mode (400 Kbps)
 - Fast-mode plus (1 Mbps)
 - High-speed mode (3.33 Mbps)
- Clock low timeout interrupt
- Dual slave address capability
- Glitch suppression
- Master and slave interrupt generation
 - Master generates interrupts when a transmit or receive operation completes (or aborts due to an error)
 - Slave generates interrupts when data has been transferred or requested by a master or when a START or STOP condition is detected
- Master with arbitration and clock synchronization, multimaster support, and 7-bit addressing mode

1.3.3.5 SSI (see page 958)

Synchronous Serial Interface (SSI) is a four-wire bi-directional communications interface that converts data between parallel and serial. The SSI module performs serial-to-parallel conversion on data received from a peripheral device, and parallel-to-serial conversion on data transmitted to a peripheral device. The SSI module can be configured as either a master or slave device. As a slave device, the SSI module can also be configured to disable its output, which allows a master device to be coupled with multiple slave devices. The TX and RX paths are buffered with separate internal FIFOs.

The SSI module also includes a programmable bit rate clock divider and prescaler to generate the output serial clock derived from the SSI module's input clock. Bit rates are generated based on the input clock and the maximum bit rate is determined by the connected peripheral.

The LM4F232H5QC microcontroller includes four SSI modules with the following features:

- Programmable interface operation for Freescale SPI, MICROWIRE, or Texas Instruments synchronous serial interfaces
- Master or slave operation
- Programmable clock bit rate and prescaler
- Separate transmit and receive FIFOs, each 16 bits wide and 8 locations deep
- Programmable data frame size from 4 to 16 bits
- Internal loopback test mode for diagnostic/debug testing
- Standard FIFO-based interrupts and End-of-Transmission interrupt
- Efficient transfers using Micro Direct Memory Access Controller (µDMA)
 - Separate channels for transmit and receive
 - Receive single request asserted when data is in the FIFO; burst request asserted when FIFO contains 4 entries
 - Transmit single request asserted when there is space in the FIFO; burst request asserted when four or more entries are available to be written in the FIFO

1.3.4 System Integration

The LM4F232H5QC microcontroller provides a variety of standard system functions integrated into the device, including:

- Direct Memory Access Controller (DMA)
- System control and clocks including on-chip precision 16-MHz oscillator
- Six 32-bit timers (up to twelve 16-bit)
- Six wide 64-bit timers (up to twelve 32-bit)
- Twelve 32/64-bit Capture Compare PWM (CCP) pins
- Lower-power battery-backed Hibernation module
- Real-Time Clock in Hibernation module
- Two Watchdog Timers
 - One timer runs off the main oscillator
 - One timer runs off the precision internal oscillator
- Up to 69 GPIOs, depending on configuration
 - Highly flexible pin muxing allows use as GPIO or one of several peripheral functions
 - Independently configurable to 2-, 4- or 8-mA drive capability
 - Up to 4 GPIOs can have 18-mA drive capability

The following sections provide more detail on each of these functions.

1.3.4.1 Direct Memory Access (see page 582)

The LM4F232H5QC microcontroller includes a Direct Memory Access (DMA) controller, known as micro-DMA (μ DMA). The μ DMA controller provides a way to offload data transfer tasks from the Cortex-M4F processor, allowing for more efficient use of the processor and the available bus bandwidth. The μ DMA controller can perform transfers between memory and peripherals. It has dedicated channels for each supported on-chip module and can be programmed to automatically perform transfers between peripherals and memory as the peripheral is ready to transfer more data. The μ DMA controller provides the following features:

- ARM PrimeCell® 32-channel configurable µDMA controller
- Support for memory-to-memory, memory-to-peripheral, and peripheral-to-memory in multiple transfer modes
 - Basic for simple transfer scenarios
 - Ping-pong for continuous data flow
 - Scatter-gather for a programmable list of up to 256 arbitrary transfers initiated from a single request
- Highly flexible and configurable channel operation
 - Independently configured and operated channels
 - Dedicated channels for supported on-chip modules
 - Flexible channel assignments
 - One channel each for receive and transmit path for bidirectional modules
 - Dedicated channel for software-initiated transfers
 - Per-channel configurable priority scheme
 - Optional software-initiated requests for any channel
- Two levels of priority
- Design optimizations for improved bus access performance between µDMA controller and the processor core
 - µDMA controller access is subordinate to core access
 - RAM striping
 - Peripheral bus segmentation
- Data sizes of 8, 16, and 32 bits
- Transfer size is programmable in binary steps from 1 to 1024
- Source and destination address increment size of byte, half-word, word, or no increment
- Maskable peripheral requests

Interrupt on transfer completion, with a separate interrupt per channel

1.3.4.2 System Control and Clocks (see page 216)

System control determines the overall operation of the device. It provides information about the device, controls power-saving features, controls the clocking of the device and individual peripherals, and handles reset detection and reporting.

- Device identification information: version, part number, SRAM size, Flash memory size, and so on
- Power control
 - On-chip fixed Low Drop-Out (LDO) voltage regulator
 - Hibernation module handles the power-up/down 3.3 V sequencing and control for the core digital logic and analog circuits
 - Low-power options for microcontroller: Sleep and Deep-sleep modes with clock gating
 - Low-power options for on-chip modules: software controls shutdown of individual peripherals and memory
 - 3.3-V supply brown-out detection and reporting via interrupt or reset
- Multiple clock sources for microcontroller system clock
 - Precision Oscillator (PIOSC): On-chip resource providing a 16 MHz ±1% frequency at room temperature
 - 16 MHz ±3% across temperature
 - Can be recalibrated with 7-bit trim resolution
 - · Software power down control for low power modes
 - Main Oscillator (MOSC): A frequency-accurate clock source by one of two means: an external single-ended clock source is connected to the OSC0 input pin, or an external crystal is connected across the OSC0 input and OSC1 output pins.
 - External crystal used with or without on-chip PLL: select supported frequencies from 4 MHz to 25 MHz.
 - · External oscillator: from DC to maximum device speed
 - Low Frequency Internal Oscillator (LFIOSC): On-chip resource used during power-saving modes
 - Hibernate RTC oscillator clock that can be configured to be the 32.768-kHz external oscillator source from the Hibernation (HIB) module or the HIB Low Frequency clock source (HIB LFIOSC), which is located within the Hibernation Module.
- Flexible reset sources
 - Power-on reset (POR)
 - Reset pin assertion
 - Brown-out reset (BOR) detector alerts to system power drops
 - Software reset

- Watchdog timer reset
- MOSC failure

1.3.4.3 Programmable Timers (see page 704)

Programmable timers can be used to count or time external events that drive the Timer input pins. Each 16/32-bit GPTM block provides two 16-bit timers/counters that can be configured to operate independently as timers or event counters, or configured to operate as one 32-bit timer or one 32-bit Real-Time Clock (RTC). Each 32/64-bit Wide GPTM block provides two 32-bit timers/counters that can be configured to operate independently as timersor event counters, or configured to operate as one 64-bit timer or one 64-bit Real-Time Clock (RTC). Timers can also be used to trigger analog-to-digital (ADC) conversions and DMA transfers.

The General-Purpose Timer Module (GPTM) contains six 16/32-bit GPTM blocks and six 32/64-bit Wide GPTM blocks with the following functional options:

- 16/32-bit operating modes:
 - 16- or 32-bit programmable one-shot timer
 - 16- or 32-bit programmable periodic timer
 - 16-bit general-purpose timer with an 8-bit prescaler
 - 32-bit Real-Time Clock (RTC) when using an external 32.768-KHz clock as the input
 - 16-bit input-edge count- or time-capture modes with an 8-bit prescaler
 - 16-bit PWM mode with an 8-bit prescaler and software-programmable output inversion of the PWM signal
- 32/64-bit operating modes:
 - 32- or 64-bit programmable one-shot timer
 - 32- or 64-bit programmable periodic timer
 - 32-bit general-purpose timer with a 16-bit prescaler
 - 64-bit Real-Time Clock (RTC) when using an external 32.768-KHz clock as the input
 - 32-bit input-edge count- or time-capture modes with a16-bit prescaler
 - 32-bit PWM mode with a 16-bit prescaler and software-programmable output inversion of the PWM signal
- Count up or down
- Twelve 16/32-bit Capture Compare PWM pins (CCP)
- Twelve 32/64-bit Capture Compare PWM pins (CCP)
- Daisy chaining of timer modules to allow a single timer to initiate multiple timing events
- Timer synchronization allows selected timers to start counting on the same clock cycle

- ADC event trigger
- User-enabled stalling when the microcontroller asserts CPU Halt flag during debug (excluding RTC mode)
- Ability to determine the elapsed time between the assertion of the timer interrupt and entry into the interrupt service routine
- Efficient transfers using Micro Direct Memory Access Controller (µDMA)
 - Dedicated channel for each timer
 - Burst request generated on timer interrupt

1.3.4.4 CCP Pins (see page 713)

Capture Compare PWM pins (CCP) can be used by the General-Purpose Timer Module to time/count external events using the CCP pin as an input. Alternatively, the GPTM can generate a simple PWM output on the CCP pin.

The LM4F232H5QC microcontroller includes twelve 16/32-bit CCP pins that can be programmed to operate in the following modes:

- Capture: The GP Timer is incremented/decremented by programmed events on the CCP input. The GP Timer captures and stores the current timer value when a programmed event occurs.
- Compare: The GP Timer is incremented/decremented by programmed events on the CCP input. The GP Timer compares the current value with a stored value and generates an interrupt when a match occurs.
- PWM: The GP Timer is incremented/decremented by the system clock. A PWM signal is generated based on a match between the counter value and a value stored in a match register and is output on the CCP pin.

1.3.4.5 Hibernation Module (HIB) (see page 491)

The Hibernation module provides logic to switch power off to the main processor and peripherals and to wake on external or time-based events. The Hibernation module includes power-sequencing logic and has the following features:

- 32-bit real-time seconds counter (RTC) with 1/32,768 second resolution and a 15-bit sub-seconds counter
 - 32-bit RTC seconds match register and a 15-bit sub seconds match for timed wake-up and interrupt generation with 1/32,768 second resolution
 - RTC predivider trim for making fine adjustments to the clock rate
- Two mechanisms for power control
 - System power control using discrete external regulator
 - On-chip power control using internal switches under register control
- Dedicated pin for waking using an external signal
- RTC operational and hibernation memory valid as long as V_{DD} or V_{BAT} is valid

- Low-battery detection, signaling, and interrupt generation, with optional wake on low battery
- GPIO pin state can be retained during hibernation
- Clock source from a 32.768-kHz external crystal or oscillator
- Sixteen 32-bit words of battery-backed memory to save state during hibernation
- Programmable interrupts for:
 - RTC match
 - External wake
 - Low battery

1.3.4.6 Watchdog Timers (see page 774)

A watchdog timer is used to regain control when a system has failed due to a software error or to the failure of an external device to respond in the expected way. The Stellaris Watchdog Timer can generate an interrupt, a non-maskable interrupt, or a reset when a time-out value is reached. In addition, the Watchdog Timer is ARM FiRM-compliant and can be configured to generate an interrupt to the microcontroller on its first time-out, and to generate a reset signal on its second timeout. Once the Watchdog Timer has been configured, the lock register can be written to prevent the timer configuration from being inadvertently altered.

The LM4F232H5QC microcontroller has two Watchdog Timer modules: Watchdog Timer 0 uses the system clock for its timer clock; Watchdog Timer 1 uses the PIOSC as its timer clock. The Stellaris Watchdog Timer module has the following features:

- 32-bit down counter with a programmable load register
- Separate watchdog clock with an enable
- Programmable interrupt generation logic with interrupt masking and optional NMI function
- Lock register protection from runaway software
- Reset generation logic with an enable/disable
- User-enabled stalling when the microcontroller asserts the CPU Halt flag during debug

1.3.4.7 Programmable GPIOs (see page 646)

General-purpose input/output (GPIO) pins offer flexibility for a variety of connections. The Stellaris GPIO module is comprised of ten physical GPIO blocks, each corresponding to an individual GPIO port. The GPIO module is FiRM-compliant (compliant to the ARM Foundation IP for Real-Time Microcontrollers specification) and supports 0-69 programmable input/output pins. The number of GPIOs available depends on the peripherals being used (see "Signal Tables" on page 1336 for the signals available to each GPIO pin).

- Up to 69 GPIOs, depending on configuration
- Highly flexible pin muxing allows use as GPIO or one of several peripheral functions
- 5-V-tolerant in input configuration

- Fast toggle capable of a change every clock cycle for ports on AHB, every two clock cycles for ports on APB
- Programmable control for GPIO interrupts
 - Interrupt generation masking
 - Edge-triggered on rising, falling, or both
 - Level-sensitive on High or Low values
- Bit masking in both read and write operations through address lines
- Can be used to initiate an ADC sample sequence or a µDMA transfer
- Pin state can be retained during Hibernation mode
- Pins configured as digital inputs are Schmitt-triggered
- Programmable control for GPIO pad configuration
 - Weak pull-up or pull-down resistors
 - 2-mA, 4-mA, and 8-mA pad drive for digital communication; up to four pads can sink 18-mA for high-current applications
 - Slew rate control for 8-mA pad drive
 - Open drain enables
 - Digital input enables

1.3.5 Advanced Motion Control

The LM4F232H5QC microcontroller provides motion control functions integrated into the device, including:

- Two PWM modules, with a total of 16 advanced PWM outputs for motion and energy applications
- Eight fault inputs to promote low-latency shutdown
- Two Quadrature Encoder Inputs (QEI)

The following provides more detail on these motion control functions.

1.3.5.1 PWM (see page 1235)

The Stellaris microcontroller contains two PWM modules, each with four PWM generator blocks and a control block, for a total of 16 PWM outputs. Pulse width modulation (PWM) is a powerful technique for digitally encoding analog signal levels. High-resolution counters are used to generate a square wave, and the duty cycle of the square wave is modulated to encode an analog signal. Typical applications include switching power supplies and motor control. Each LM4F232H5QC PWM module consists of four PWM generator block and a control block. Each PWM generator block contains one timer (16-bit down or up/down counter), two comparators, a PWM signal generator, a dead-band generator, and an interrupt/ADC-trigger selector. Each PWM generator block produces

two PWM signals that can either be independent signals or a single pair of complementary signals with dead-band delays inserted.

Each PWM generator has the following features:

- Four fault-condition handling inputs to quickly provide low-latency shutdown and prevent damage to the motor being controlled, for a total of eight inputs
- One 16-bit counter
 - Runs in Down or Up/Down mode
 - Output frequency controlled by a 16-bit load value
 - Load value updates can be synchronized
 - Produces output signals at zero and load value
- Two PWM comparators
 - Comparator value updates can be synchronized
 - Produces output signals on match
- PWM signal generator
 - Output PWM signal is constructed based on actions taken as a result of the counter and PWM comparator output signals
 - Produces two independent PWM signals
- Dead-band generator
 - Produces two PWM signals with programmable dead-band delays suitable for driving a half-H bridge
 - Can be bypassed, leaving input PWM signals unmodified
- Can initiate an ADC sample sequence

The control block determines the polarity of the PWM signals and which signals are passed through to the pins. The output of the PWM generation blocks are managed by the output control block before being passed to the device pins. The PWM control block has the following options:

- PWM output enable of each PWM signal
- Optional output inversion of each PWM signal (polarity control)
- Optional fault handling for each PWM signal
- Synchronization of timers in the PWM generator blocks
- Synchronization of timer/comparator updates across the PWM generator blocks
- Extended PWM synchronization of timer/comparator updates across the PWM generator blocks
- Interrupt status summary of the PWM generator blocks

- Extended PWM fault handling, with multiple fault signals, programmable polarities, and filtering
- PWM generators can be operated independently or synchronized with other generators

1.3.5.2 QEI (see page 1313)

A quadrature encoder, also known as a 2-channel incremental encoder, converts linear displacement into a pulse signal. By monitoring both the number of pulses and the relative phase of the two signals, the position, direction of rotation, and speed can be tracked. In addition, a third channel, or index signal, can be used to reset the position counter. The Stellaris quadrature encoder with index (QEI) module interprets the code produced by a quadrature encoder wheel to integrate position over time and determine direction of rotation. In addition, it can capture a running estimate of the velocity of the encoder wheel. The input frequency of the QEI inputs may be as high as 1/4 of the processor frequency (for example, 20 MHz for a 80-MHz system).

The LM4F232H5QC microcontroller includes two QEI modules providing control of two motors at the same time with the following features:

- Position integrator that tracks the encoder position
- Programmable noise filter on the inputs
- Velocity capture using built-in timer
- The input frequency of the QEI inputs may be as high as 1/4 of the processor frequency (for example, 12.5 MHz for a 50-MHz system)
- Interrupt generation on:
 - Index pulse
 - Velocity-timer expiration
 - Direction change
 - Quadrature error detection

1.3.6 Analog

The LM4F232H5QC microcontroller provides analog functions integrated into the device, including:

- Two 12-bit Analog-to-Digital Converters (ADC) with 22 analog input channels and a sample rate of one million samples/second
- Three analog comparators
- 16 digital comparators
- On-chip voltage regulator

The following provides more detail on these analog functions.

1.3.6.1 ADC (see page 799)

An analog-to-digital converter (ADC) is a peripheral that converts a continuous analog voltage to a discrete digital number. The Stellaris ADC module features 12-bit conversion resolution and supports 22 input channels plus an internal temperature sensor. Four buffered sample sequencers allow

rapid sampling of up to 22 analog input sources without controller intervention. Each sample sequencer provides flexible programming with fully configurable input source, trigger events, interrupt generation, and sequencer priority. Each ADC module has a digital comparator function that allows the conversion value to be diverted to a comparison unit that provides eight digital comparators.

The LM4F232H5QC microcontroller provides two ADC modules with the following features:

- 22 shared analog input channels
- 12-bit precision ADC
- Single-ended and differential-input configurations
- On-chip internal temperature sensor
- Maximum sample rate of one million samples/second
- Optional phase shift in sample time programmable from 22.5° to 337.5°
- Four programmable sample conversion sequencers from one to eight entries long, with corresponding conversion result FIFOs
- Flexible trigger control
 - Controller (software)
 - Timers
 - Analog Comparators
 - PWM
 - GPIO
- Hardware averaging of up to 64 samples
- Digital comparison unit providing eight digital comparators
- Converter uses two external reference signals or VDDA and GNDA as the voltage reference
- Power and ground for the analog circuitry is separate from the digital power and ground
- Efficient transfers using Micro Direct Memory Access Controller (µDMA)
 - Dedicated channel for each sample sequencer
 - ADC module uses burst requests for DMA

1.3.6.2 Analog Comparators (see page 1219)

An analog comparator is a peripheral that compares two analog voltages and provides a logical output that signals the comparison result. The LM4F232H5QC microcontroller provides three independent integrated analog comparators that can be configured to drive an output or generate an interrupt or ADC event.

The comparator can provide its output to a device pin, acting as a replacement for an analog comparator on the board, or it can be used to signal the application via interrupts or triggers to the

ADC to cause it to start capturing a sample sequence. The interrupt generation and ADC triggering logic is separate. This means, for example, that an interrupt can be generated on a rising edge and the ADC triggered on a falling edge.

The LM4F232H5QC microcontroller provides three independent integrated analog comparators with the following functions:

- Compare external pin input to external pin input or to internal programmable voltage reference
- Compare a test voltage against any one of the following voltages:
 - An individual external reference voltage
 - A shared single external reference voltage
 - A shared internal reference voltage

1.3.7 JTAG and ARM Serial Wire Debug (see page 204)

The Joint Test Action Group (JTAG) port is an IEEE standard that defines a Test Access Port and Boundary Scan Architecture for digital integrated circuits and provides a standardized serial interface for controlling the associated test logic. The TAP, Instruction Register (IR), and Data Registers (DR) can be used to test the interconnections of assembled printed circuit boards and obtain manufacturing information on the components. The JTAG Port also provides a means of accessing and controlling design-for-test features such as I/O pin observation and control, scan testing, and debugging. Texas Instruments replaces the ARM SW-DP and JTAG-DP with the ARM Serial Wire JTAG Debug Port (SWJ-DP) interface. The SWJ-DP interface combines the SWD and JTAG debug ports into one module providing all the normal JTAG debug and test functionality plus real-time access to system memory without halting the core or requiring any target resident code. The SWJ-DP interface has the following features:

- IEEE 1149.1-1990 compatible Test Access Port (TAP) controller
- Four-bit Instruction Register (IR) chain for storing JTAG instructions
- IEEE standard instructions: BYPASS, IDCODE, SAMPLE/PRELOAD, EXTEST and INTEST
- ARM additional instructions: APACC, DPACC and ABORT
- Integrated ARM Serial Wire Debug (SWD)
 - Serial Wire JTAG Debug Port (SWJ-DP)
 - Flash Patch and Breakpoint (FPB) unit for implementing breakpoints
 - Data Watchpoint and Trace (DWT) unit for implementing watchpoints, trigger resources, and system profiling
 - Instrumentation Trace Macrocell (ITM) for support of printf style debugging
 - Embedded Trace Macrocell (ETM) for instruction trace capture
 - Trace Port Interface Unit (TPIU) for bridging to a Trace Port Analyzer

1.3.8 Packaging and Temperature

■ Industrial-range (-40°C to 85°C) 100-pin RoHS-compliant LQFP package

1.4 LM4F232H5QC Microcontroller Hardware Details

Details on the pins and package can be found in the following sections:

- "Pin Diagram" on page 1335
- "Signal Tables" on page 1336
- "Operating Characteristics" on page 1376
- "Electrical Characteristics" on page 1376
- "Package Information" on page 1417

2 The Cortex-M4F Processor

The ARM® Cortex[™]-M4F processor provides a high-performance, low-cost platform that meets the system requirements of minimal memory implementation, reduced pin count, and low power consumption, while delivering outstanding computational performance and exceptional system response to interrupts. Features include:

- 32-bit ARM[®] Cortex[™]-M4F architecture optimized for small-footprint embedded applications
- 80-MHz operation; 100 DMIPS performance
- Outstanding processing performance combined with fast interrupt handling
- Thumb-2 mixed 16-/32-bit instruction set delivers the high performance expected of a 32-bit ARM core in a compact memory size usually associated with 8- and 16-bit devices, typically in the range of a few kilobytes of memory for microcontroller-class applications
 - Single-cycle multiply instruction and hardware divide
 - Atomic bit manipulation (bit-banding), delivering maximum memory utilization and streamlined peripheral control
 - Unaligned data access, enabling data to be efficiently packed into memory
- IEEE754-compliant single-precision Floating-Point Unit (FPU)
- 16-bit SIMD vector processing unit
- Fast code execution permits slower processor clock or increases sleep mode time
- Harvard architecture characterized by separate buses for instruction and data
- Efficient processor core, system and memories
- Hardware division and fast digital-signal-processing orientated multiply accumulate
- Saturating arithmetic for signal processing
- Deterministic, high-performance interrupt handling for time-critical applications
- Memory protection unit (MPU) to provide a privileged mode for protected operating system functionality
- Enhanced system debug with extensive breakpoint and trace capabilities
- Serial Wire Debug and Serial Wire Trace reduce the number of pins required for debugging and tracing
- Migration from the ARM7 processor family for better performance and power efficiency
- Optimized for single-cycle Flash memory usage up to specific frequencies; see "Internal Memory" on page 522 for more information.
- Ultra-low power consumption with integrated sleep modes

The Stellaris® family of microcontrollers builds on this core to bring high-performance 32-bit computing to

This chapter provides information on the Stellaris implementation of the Cortex-M4F processor, including the programming model, the memory model, the exception model, fault handling, and power management.

For technical details on the instruction set, see the *Cortex*™-*M3/M4 Instruction Set Technical User's Manual.*

2.1 Block Diagram

The Cortex-M4F processor is built on a high-performance processor core, with a 3-stage pipeline Harvard architecture, making it ideal for demanding embedded applications. The processor delivers exceptional power efficiency through an efficient instruction set and extensively optimized design, providing high-end processing hardware including IEEE754-compliant single-precision floating-point computation, a range of single-cycle and SIMD multiplication and multiply-with-accumulate capabilities, saturating arithmetic and dedicated hardware division.

To facilitate the design of cost-sensitive devices, the Cortex-M4F processor implements tightly coupled system components that reduce processor area while significantly improving interrupt handling and system debug capabilities. The Cortex-M4F processor implements a version of the Thumb® instruction set based on Thumb-2 technology, ensuring high code density and reduced program memory requirements. The Cortex-M4F instruction set provides the exceptional performance expected of a modern 32-bit architecture, with the high code density of 8-bit and 16-bit microcontrollers.

The Cortex-M4F processor closely integrates a nested interrupt controller (NVIC), to deliver industry-leading interrupt performance. The Stellaris NVIC includes a non-maskable interrupt (NMI) and provides eight interrupt priority levels. The tight integration of the processor core and NVIC provides fast execution of interrupt service routines (ISRs), dramatically reducing interrupt latency. The hardware stacking of registers and the ability to suspend load-multiple and store-multiple operations further reduce interrupt latency. Interrupt handlers do not require any assembler stubs which removes code overhead from the ISRs. Tail-chaining optimization also significantly reduces the overhead when switching from one ISR to another. To optimize low-power designs, the NVIC integrates with the sleep modes, including Deep-sleep mode, which enables the entire device to be rapidly powered down.




Figure 2-1. CPU Block Diagram

2.2 Overview

2.2.1 System-Level Interface

The Cortex-M4F processor provides multiple interfaces using AMBA® technology to provide high-speed, low-latency memory accesses. The core supports unaligned data accesses and implements atomic bit manipulation that enables faster peripheral controls, system spinlocks, and thread-safe Boolean data handling.

The Cortex-M4F processor has a memory protection unit (MPU) that provides fine-grain memory control, enabling applications to implement security privilege levels and separate code, data and stack on a task-by-task basis.

2.2.2 Integrated Configurable Debug

The Cortex-M4F processor implements a complete hardware debug solution, providing high system visibility of the processor and memory through either a traditional JTAG port or a 2-pin Serial Wire Debug (SWD) port that is ideal for microcontrollers and other small package devices. The Stellaris implementation replaces the ARM SW-DP and JTAG-DP with the ARM CoreSight™-compliant Serial Wire JTAG Debug Port (SWJ-DP) interface. The SWJ-DP interface combines the SWD and JTAG debug ports into one module. See the *ARM® Debug Interface V5 Architecture Specification* for details on SWJ-DP.

For system trace, the processor integrates an Instrumentation Trace Macrocell (ITM) alongside data watchpoints and a profiling unit. To enable simple and cost-effective profiling of the system trace events, a Serial Wire Viewer (SWV) can export a stream of software-generated messages, data trace, and profiling information through a single pin.

The Embedded Trace Macrocell (ETM) delivers unrivaled instruction trace capture in an area smaller than traditional trace units, enabling full instruction trace. For more details on the ARM ETM, see the ARM® Embedded Trace Macrocell Architecture Specification.

The Flash Patch and Breakpoint Unit (FPB) provides up to eight hardware breakpoint comparators that debuggers can use. The comparators in the FPB also provide remap functions of up to eight words in the program code in the CODE memory region. This enables applications stored in a read-only area of Flash memory to be patched in another area of on-chip SRAM or Flash memory. If a patch is required, the application programs the FPB to remap a number of addresses. When those addresses are accessed, the accesses are redirected to a remap table specified in the FPB configuration.

For more information on the Cortex-M4F debug capabilities, see the ARM® Debug Interface V5 Architecture Specification.

2.2.3 Trace Port Interface Unit (TPIU)

The TPIU acts as a bridge between the Cortex-M4F trace data from the ITM, and an off-chip Trace Port Analyzer, as shown in Figure 2-2 on page 76.

Debug Serial Wire **ATB** Trace Out ATB Asynchronous FIFO Trace Port Interface (serializer) Slave (SWO) Port APB APB Slave -Interface Port

Figure 2-2. TPIU Block Diagram

2.2.4 Cortex-M4F System Component Details

The Cortex-M4F includes the following system components:

■ SysTick

A 24-bit count-down timer that can be used as a Real-Time Operating System (RTOS) tick timer or as a simple counter (see "System Timer (SysTick)" on page 127).

Nested Vectored Interrupt Controller (NVIC)

An embedded interrupt controller that supports low latency interrupt processing (see "Nested Vectored Interrupt Controller (NVIC)" on page 128).

■ System Control Block (SCB)

The programming model interface to the processor. The SCB provides system implementation information and system control, including configuration, control, and reporting of system exceptions (see "System Control Block (SCB)" on page 129).

■ Memory Protection Unit (MPU)

Improves system reliability by defining the memory attributes for different memory regions. The MPU provides up to eight different regions and an optional predefined background region (see "Memory Protection Unit (MPU)" on page 129).

■ Floating-Point Unit (FPU)

Fully supports single-precision add, subtract, multiply, divide, multiply and accumulate, and square-root operations. It also provides conversions between fixed-point and floating-point data formats, and floating-point constant instructions.

2.3 Programming Model

This section describes the Cortex-M4F programming model. In addition to the individual core register descriptions, information about the processor modes and privilege levels for software execution and stacks is included.

2.3.1 Processor Mode and Privilege Levels for Software Execution

The Cortex-M4F has two modes of operation:

Thread mode

Used to execute application software. The processor enters Thread mode when it comes out of reset.

Handler mode

Used to handle exceptions. When the processor has finished exception processing, it returns to Thread mode.

In addition, the Cortex-M4F has two privilege levels:

Unprivileged

In this mode, software has the following restrictions:

- Limited access to the MSR and MRS instructions and no use of the CPS instruction.
- No access to the system timer, NVIC, or system control block
- Possibly restricted access to memory or peripherals

Privileged

In this mode, software can use all the instructions and has access to all resources.

In Thread mode, the **CONTROL** register (see page 92) controls whether software execution is privileged or unprivileged. In Handler mode, software execution is always privileged.

Only privileged software can write to the **CONTROL** register to change the privilege level for software execution in Thread mode. Unprivileged software can use the SVC instruction to make a supervisor call to transfer control to privileged software.

2.3.2 Stacks

The processor uses a full descending stack, meaning that the stack pointer indicates the last stacked item on the memory. When the processor pushes a new item onto the stack, it decrements the stack pointer and then writes the item to the new memory location. The processor implements two stacks: the main stack and the process stack, with a pointer for each held in independent registers (see the **SP** register on page 82).

In Thread mode, the **CONTROL** register (see page 92) controls whether the processor uses the main stack or the process stack. In Handler mode, the processor always uses the main stack. The options for processor operations are shown in Table 2-1 on page 78.

Table 2-1. Summary of Processor Mode, Privilege Level, and Stack Use

Processor Mode	Use	Privilege Level	Stack Used
Thread	Applications	Privileged or unprivileged ^a	Main stack or process stack a
Handler	Exception handlers	Always privileged	Main stack

a. See CONTROL (page 92).

2.3.3 Register Map

Figure 2-3 on page 79 shows the Cortex-M4F register set. Table 2-2 on page 79 lists the Core registers. The core registers are not memory mapped and are accessed by register name, so the base address is n/a (not applicable) and there is no offset.




Figure 2-3. Cortex-M4F Register Set

Table 2-2. Processor Register Map

abio 2 2.1 1 0000001 Rogistor inap						
Offset	Name	Туре	Reset	Description	See page	
-	R0	R/W	-	Cortex General-Purpose Register 0	81	
-	R1	R/W	-	Cortex General-Purpose Register 1	81	
-	R2	R/W	-	Cortex General-Purpose Register 2	81	
-	R3	R/W	-	Cortex General-Purpose Register 3	81	
-	R4	R/W	-	Cortex General-Purpose Register 4	81	
-	R5	R/W	-	Cortex General-Purpose Register 5	81	
-	R6	R/W	-	Cortex General-Purpose Register 6	81	
-	R7	R/W	-	Cortex General-Purpose Register 7	81	
-	R8	R/W	-	Cortex General-Purpose Register 8	81	
-	R9	R/W	-	Cortex General-Purpose Register 9	81	
-	R10	R/W	-	Cortex General-Purpose Register 10	81	
-	R11	R/W	-	Cortex General-Purpose Register 11	81	

Table 2-2. Processor Register Map (continued)

Offset	Name	Туре	Reset	Description	See page
-	R12	R/W	-	Cortex General-Purpose Register 12	81
-	SP	R/W	-	Stack Pointer	82
-	LR	R/W	0xFFFF.FFFF	Link Register	83
-	PC	R/W	-	Program Counter	84
-	PSR	R/W	0x0100.0000	Program Status Register	85
-	PRIMASK	R/W	0x0000.0000	Priority Mask Register	89
-	FAULTMASK	R/W	0x0000.0000	Fault Mask Register	90
-	BASEPRI	R/W	0x0000.0000	Base Priority Mask Register	91
-	CONTROL	R/W	0x0000.0000	Control Register	92
-	FPSC	R/W	-	Floating-Point Status Control	94

2.3.4 Register Descriptions

This section lists and describes the Cortex-M4F registers, in the order shown in Figure 2-3 on page 79. The core registers are not memory mapped and are accessed by register name rather than offset.

Note: The register type shown in the register descriptions refers to type during program execution in Thread mode and Handler mode. Debug access can differ.

Register 1: Cortex General-Purpose Register 0 (R0)

Register 2: Cortex General-Purpose Register 1 (R1)

Register 3: Cortex General-Purpose Register 2 (R2)

Register 4: Cortex General-Purpose Register 3 (R3)

Register 5: Cortex General-Purpose Register 4 (R4)

Register 6: Cortex General-Purpose Register 5 (R5)

Register 7: Cortex General-Purpose Register 6 (R6)

Register 8: Cortex General-Purpose Register 7 (R7)

Register 9: Cortex General-Purpose Register 8 (R8)

Register 10: Cortex General-Purpose Register 9 (R9)

Register 11: Cortex General-Purpose Register 10 (R10)


Register 12: Cortex General-Purpose Register 11 (R11)

Register 13: Cortex General-Purpose Register 12 (R12)

The **Rn** registers are 32-bit general-purpose registers for data operations and can be accessed from either privileged or unprivileged mode.


Cortex General-Purpose Register 0 (R0)





Register 14: Stack Pointer (SP)

The **Stack Pointer (SP)** is register R13. In Thread mode, the function of this register changes depending on the ASP bit in the **Control Register (CONTROL)** register. When the ASP bit is clear, this register is the **Main Stack Pointer (MSP)**. When the ASP bit is set, this register is the **Process Stack Pointer (PSP)**. On reset, the ASP bit is clear, and the processor loads the **MSP** with the value from address 0x0000.0000. The **MSP** can only be accessed in privileged mode; the **PSP** can be accessed in either privileged or unprivileged mode.




Register 15: Link Register (LR)

The **Link Register (LR)** is register R14, and it stores the return information for subroutines, function calls, and exceptions. **LR** can be accessed from either privileged or unprivileged mode.

 ${\tt EXC_RETURN}$ is loaded into **LR** on exception entry. See Table 2-10 on page 115 for the values and description.

Link Register (LR)

Type R/W, reset 0xFFFF.FFF



Bit/Field Name Type Reset Description


31:0 LINK R/W 0xFFF.FFF This field is the return address.

Register 16: Program Counter (PC)

The **Program Counter (PC)** is register R15, and it contains the current program address. On reset, the processor loads the **PC** with the value of the reset vector, which is at address 0x0000.0004. Bit 0 of the reset vector is loaded into the THUMB bit of the **EPSR** at reset and must be 1. The **PC** register can be accessed in either privileged or unprivileged mode.

Program Counter (PC)





Bit/Field	Name	Type	Reset	Description
31:0	PC	R/W	_	This field is the current program address.

Register 17: Program Status Register (PSR)

Note: This register is also referred to as **xPSR**.

The **Program Status Register (PSR)** has three functions, and the register bits are assigned to the different functions:

- Application Program Status Register (APSR), bits 31:27, bits 19:16
- Execution Program Status Register (EPSR), bits 26:24, 15:10
- Interrupt Program Status Register (IPSR), bits 7:0

The **PSR**, **IPSR**, and **EPSR** registers can only be accessed in privileged mode; the **APSR** register can be accessed in either privileged or unprivileged mode.

APSR contains the current state of the condition flags from previous instruction executions.

EPSR contains the Thumb state bit and the execution state bits for the If-Then (IT) instruction or the Interruptible-Continuable Instruction (ICI) field for an interrupted load multiple or store multiple instruction. Attempts to read the **EPSR** directly through application software using the MSR instruction always return zero. Attempts to write the **EPSR** using the MSR instruction in application software are always ignored. Fault handlers can examine the **EPSR** value in the stacked **PSR** to determine the operation that faulted (see "Exception Entry and Return" on page 112).

IPSR contains the exception type number of the current Interrupt Service Routine (ISR).

These registers can be accessed individually or as a combination of any two or all three registers, using the register name as an argument to the MSR or MRS instructions. For example, all of the registers can be read using **PSR** with the MRS instruction, or **APSR** only can be written to using **APSR** with the MSR instruction. page 85 shows the possible register combinations for the **PSR**. See the MRS and MSR instruction descriptions in the *Cortex™-M3/M4 Instruction Set Technical User's Manual* for more information about how to access the program status registers.


Table 2-3. PSR Register Combinations

Register	Туре	Combination
PSR	R/W ^{a, b}	APSR, EPSR, and IPSR
IEPSR	RO	EPSR and IPSR
IAPSR	R/W ^a	APSR and IPSR
EAPSR	R/W ^b	APSR and EPSR

- a. The processor ignores writes to the IPSR bits.
- b. Reads of the EPSR bits return zero, and the processor ignores writes to these bits.

Program Status Register (PSR)

Type R/W, reset 0x0100.0000



Bit/Field	Name	Туре	Reset	Description
31	N	R/W	0	APSR Negative or Less Flag
				Value Description
				 The previous operation result was negative or less than. The previous operation result was positive, zero, greater than,
				0 The previous operation result was positive, zero, greater than, or equal.
				The value of this bit is only meaningful when accessing PSR or APSR .
30	Z	R/W	0	APSR Zero Flag
				Value Description
				1 The previous operation result was zero.
				The previous operation result was non-zero.
				The value of this bit is only meaningful when accessing PSR or APSR .
29	С	R/W	0	APSR Carry or Borrow Flag
				Value Description
				The previous add operation resulted in a carry bit or the previous subtract operation did not result in a borrow bit.
				The previous add operation did not result in a carry bit or the previous subtract operation resulted in a borrow bit.
				The value of this bit is only meaningful when accessing PSR or APSR .
28	V	R/W	0	APSR Overflow Flag
				Value Description
				1 The previous operation resulted in an overflow.
				O The previous operation did not result in an overflow.
				The value of this bit is only meaningful when accessing PSR or APSR .
27	Q	R/W	0	APSR DSP Overflow and Saturation Flag
				Value Description
				1 DSP Overflow or saturation has occurred.
				0 DSP overflow or saturation has not occurred since reset or since the bit was last cleared.
				The value of this bit is only meaningful when accessing PSR or APSR .
				This bit is cleared by software using an MRS instruction.

86 February 20, 2013

Bit/Field	Name	Туре	Reset	Description
26:25	ICI / IT	RO	0x0	EPSR ICI / IT status These bits, along with bits 15:10, contain the Interruptible-Continuable Instruction (ICI) field for an interrupted load multiple or store multiple instruction or the execution state bits of the IT instruction. When EPSR holds the ICI execution state, bits 26:25 are zero. The If-Then block contains up to four instructions following an IT instruction. Each instruction in the block is conditional. The conditions for the instructions are either all the same, or some can be the inverse of others. See the Cortex™-M3/M4 Instruction Set Technical User's Manual for more information. The value of this field is only meaningful when accessing PSR or EPSR.
24	THUMB	RO	1	EPSR Thumb State This bit indicates the Thumb state and should always be set. The following can clear the THUMB bit: ■ The BLX, BX and POP{PC} instructions ■ Restoration from the stacked xPSR value on an exception return ■ Bit 0 of the vector value on an exception entry or reset
				Attempting to execute instructions when this bit is clear results in a fault or lockup. See "Lockup" on page 117 for more information. The value of this bit is only meaningful when accessing PSR or EPSR.
23:20	reserved	RO	0x00	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
19:16	GE	R/W	0x0	Greater Than or Equal Flags See the description of the SEL instruction in the Cortex™-M3/M4 Instruction Set Technical User's Manual for more information. The value of this field is only meaningful when accessing PSR or APSR.
15:10	ICI / IT	RO	0x0	These bits, along with bits 26:25, contain the Interruptible-Continuable Instruction (ICI) field for an interrupted load multiple or store multiple instruction or the execution state bits of the IT instruction. When an interrupt occurs during the execution of an LDM, STM, PUSH POP, VLDM, VSTM, VPUSH, or VPOP instruction, the processor stops the load multiple or store multiple instruction operation temporarily and stores the next register operand in the multiple operation to bits 15:12. After servicing the interrupt, the processor returns to the register pointed to by bits 15:12 and resumes execution of the multiple load or store instruction. When EPSR holds the ICI execution state, bits 11:10 are zero. The If-Then block contains up to four instructions following a 16-bit IT instruction. Each instruction in the block is conditional. The conditions for the instructions are either all the same, or some can be the inverse of others. See the Cortex™-M3/M4 Instruction Set Technical User's Manual for more information. The value of this field is only meaningful when accessing PSR or EPSR.
9:8	reserved	RO	0x0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.

February 20, 2013 87

Bit/Field	Name	Туре	Reset	Descriptio	n
7:0	ISRNUM	RO	0x00	IPSR ISR	Number contains the exception type number of the current Interrupt
					outine (ISR).
				Value	Description
				0x00	Thread mode
				0x01	Reserved
				0x02	NMI
				0x03	Hard fault
				0x04	Memory management fault
				0x05	Bus fault
				0x06	Usage fault
				0x07-0x0	A Reserved
				0x0B	SVCall
				0x0C	Reserved for Debug
				0x0D	Reserved
				0x0E	PendSV
				0x0F	SysTick
				0x10	Interrupt Vector 0
				0x11	Interrupt Vector 1
				0x9A	Interrupt Vector 138
				See "Exce	ention Types" on page 106 for more information

See "Exception Types" on page 106 for more information.


The value of this field is only meaningful when accessing PSR or IPSR.

Register 18: Priority Mask Register (PRIMASK)

The **PRIMASK** register prevents activation of all exceptions with programmable priority. Reset, non-maskable interrupt (NMI), and hard fault are the only exceptions with fixed priority. Exceptions should be disabled when they might impact the timing of critical tasks. This register is only accessible in privileged mode. The MSR and MRS instructions are used to access the **PRIMASK** register, and the CPS instruction may be used to change the value of the **PRIMASK** register. See the Cortex™-M3/M4 Instruction Set Technical User's Manual for more information on these instructions. For more information on exception priority levels, see "Exception Types" on page 106.

Priority Mask Register (PRIMASK)

Type R/W, reset 0x0000.0000



Bit/Field	Name	Type	Reset	Description
31:1	reserved	RO	0x0000.000	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
0	PRIMASK	R/W	0	Priority Mask

Value Description


- Prevents the activation of all exceptions with configurable priority.
- 0 No effect.

Register 19: Fault Mask Register (FAULTMASK)

The **FAULTMASK** register prevents activation of all exceptions except for the Non-Maskable Interrupt (NMI). Exceptions should be disabled when they might impact the timing of critical tasks. This register is only accessible in privileged mode. The MSR and MRS instructions are used to access the **FAULTMASK** register, and the CPS instruction may be used to change the value of the **FAULTMASK** register. See the *Cortex™-M3/M4 Instruction Set Technical User's Manual* for more information on these instructions. For more information on exception priority levels, see "Exception Types" on page 106.

Fault Mask Register (FAULTMASK)

Type R/W, reset 0x0000.0000



Bit/Field	Name	Type	Reset	Description
31:1	reserved	RO	0x0000.000	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
0	FAULTMASK	R/W	0	Fault Mask

Value Description

- 1 Prevents the activation of all exceptions except for NMI.
- 0 No effect.

The processor clears the FAULTMASK bit on exit from any exception handler except the NMI handler.

Register 20: Base Priority Mask Register (BASEPRI)

The **BASEPRI** register defines the minimum priority for exception processing. When **BASEPRI** is set to a nonzero value, it prevents the activation of all exceptions with the same or lower priority level as the **BASEPRI** value. Exceptions should be disabled when they might impact the timing of critical tasks. This register is only accessible in privileged mode. For more information on exception priority levels, see "Exception Types" on page 106.

Base Priority Mask Register (BASEPRI)


Type R/W, reset 0x0000.0000

4:0

reserved

RO

0x0



Bit/Field	Name	Туре	Reset	Description
31:8	reserved	RO	0x0000.00	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
7:5	BASEPRI	R/W	0x0	Base Priority

Any exception that has a programmable priority level with the same or lower priority as the value of this field is masked. The **PRIMASK** register can be used to mask all exceptions with programmable priority levels. Higher priority exceptions have lower priority levels.

Value Description 0x0 All exceptions are unmasked. 0x1 All exceptions with priority level 1-7 are masked. 0x2 All exceptions with priority level 2-7 are masked. 0x3 All exceptions with priority level 3-7 are masked. All exceptions with priority level 4-7 are masked. 0x4 All exceptions with priority level 5-7 are masked. 0x5 All exceptions with priority level 6-7 are masked. 0x60x7 All exceptions with priority level 7 are masked.

Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.

Register 21: Control Register (CONTROL)


The **CONTROL** register controls the stack used and the privilege level for software execution when the processor is in Thread mode, and indicates whether the FPU state is active. This register is only accessible in privileged mode.

Handler mode always uses **MSP**, so the processor ignores explicit writes to the ASP bit of the **CONTROL** register when in Handler mode. The exception entry and return mechanisms automatically update the **CONTROL** register based on the EXC_RETURN value (see Table 2-10 on page 115). In an OS environment, threads running in Thread mode should use the process stack and the kernel and exception handlers should use the main stack. By default, Thread mode uses **MSP**. To switch the stack pointer used in Thread mode to **PSP**, either use the MSR instruction to set the ASP bit, as detailed in the *Cortex*[™]-*M3/M4 Instruction Set Technical User's Manual*, or perform an exception return to Thread mode with the appropriate EXC_RETURN value, as shown in Table 2-10 on page 115.

Note: When changing the stack pointer, software must use an ISB instruction immediately after the MSR instruction, ensuring that instructions after the ISB execute use the new stack pointer. See the *Cortex*TM-*M3/M4 Instruction Set Technical User's Manual*.

Control Register (CONTROL)

Type R/W, reset 0x0000.0000



Bit/Field	Name	Type	Reset	Description
31:3	reserved	RO	0x0000.000	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
2	FPCA	R/W	0	Floating-Point Context Active

Value Description

1 Floating-point context active

0 No floating-point context active

The Cortex-M4F uses this bit to determine whether to preserve floating-point state when processing an exception.

Important: Two bits control when FPCA can be enabled: the ASPEN bit in the Floating-Point Context Control (FPCC) register and the DISFPCA bit in the Auxiliary Control (ACTLR) register.

Bit/Field	Name	Туре	Reset	Description
1	ASP	R/W	0	Active Stack Pointer
				Value Description 1
0	TMPL	R/W	0	Thread Mode Privilege Level Value Description 1 Unprivileged software can be executed in Thread mode. Only privileged software can be executed in Thread mode.

February 20, 2013 93

Register 22: Floating-Point Status Control (FPSC)

The **FPSC** register provides all necessary user-level control of the floating-point system.

Floating-Point Status Control (FPSC)

Type R/W, reset -

	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16
	N	Z	С	٧	reserved	AHP	DN	FZ	RMC	ODE			rese	rved		
Type	R/W	R/W	R/W	R/W	RO	R/W	R/W	R/W	R/W	R/W	RO	RO	RO	RO	RO	RO
Reset	-	-	-	-	0	-	-	-	-	-	0	0	0	0	0	0
	15	14	13	12	11	10	9	8	7	6	5	4	3	2	1	0
	reserved				IDC	rese	rved	IXC	UFC	OFC	DZC	IOC				
Type	RO	RO	RO	RO	RO	RO	RO	RO	R/W	RO	RO	R/W	R/W	R/W	R/W	R/W
Reset	0	0	0	0	0	0	0	0	-	0	0	-	-	-	-	-

Bit/Field	Name	Туре	Reset	Description
31	N	R/W	-	Negative Condition Code Flag Floating-point comparison operations update this condition code flag.
30	Z	R/W	-	Zero Condition Code Flag Floating-point comparison operations update this condition code flag.
29	С	R/W	-	Carry Condition Code Flag Floating-point comparison operations update this condition code flag.
28	V	R/W	-	Overflow Condition Code Flag Floating-point comparison operations update this condition code flag.
27	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
26	АНР	R/W	-	Alternative Half-Precision When set, alternative half-precision format is selected. When clear, IEEE half-precision format is selected. The AHP bit in the FPDSC register holds the default value for this bit.
25	DN	R/W	-	Default NaN Mode When set, any operation involving one or more NaNs returns the Default NaN. When clear, NaN operands propagate through to the output of a floating-point operation. The DN bit in the FPDSC register holds the default value for this bit.
24	FZ	R/W	-	Flush-to-Zero Mode When set, Flush-to-Zero mode is enabled. When clear, Flush-to-Zero mode is disabled and the behavior of the floating-point system is fully compliant with the IEEE 754 standard. The FZ bit in the FPDSC register holds the default value for this bit.

Bit/Field	Name	Туре	Reset	Description
23:22	RMODE	R/W	-	Rounding Mode The specified rounding mode is used by almost all floating-point instructions. The RMODE bit in the FPDSC register holds the default value for this bit. Value Description 0x0 Round to Nearest (RN) mode 0x1 Round towards Plus Infinity (RP) mode 0x2 Round towards Minus Infinity (RM) mode 0x3 Round towards Zero (RZ) mode
21:8	reserved	RO	0x0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
7	IDC	R/W	-	Input Denormal Cumulative Exception When set, indicates this exception has occurred since 0 was last written to this bit.
6:5	reserved	RO	0x0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
4	IXC	R/W	-	Inexact Cumulative Exception When set, indicates this exception has occurred since 0 was last written to this bit.
3	UFC	R/W	-	Underflow Cumulative Exception When set, indicates this exception has occurred since 0 was last written to this bit.
2	OFC	R/W	-	Overflow Cumulative Exception When set, indicates this exception has occurred since 0 was last written to this bit.
1	DZC	R/W	-	Division by Zero Cumulative Exception When set, indicates this exception has occurred since 0 was last written to this bit.
0	IOC	R/W	-	Invalid Operation Cumulative Exception When set, indicates this exception has occurred since 0 was last written to this bit.

February 20, 2013 95

2.3.5 Exceptions and Interrupts

The Cortex-M4F processor supports interrupts and system exceptions. The processor and the Nested Vectored Interrupt Controller (NVIC) prioritize and handle all exceptions. An exception changes the normal flow of software control. The processor uses Handler mode to handle all exceptions except for reset. See "Exception Entry and Return" on page 112 for more information.

The NVIC registers control interrupt handling. See "Nested Vectored Interrupt Controller (NVIC)" on page 128 for more information.

2.3.6 Data Types

The Cortex-M4F supports 32-bit words, 16-bit halfwords, and 8-bit bytes. The processor also supports 64-bit data transfer instructions. All instruction and data memory accesses are little endian. See "Memory Regions, Types and Attributes" on page 99 for more information.

2.4 Memory Model

This section describes the processor memory map, the behavior of memory accesses, and the bit-banding features. The processor has a fixed memory map that provides up to 4 GB of addressable memory.

The memory map for the LM4F232H5QC controller is provided in Table 2-4 on page 96. In this manual, register addresses are given as a hexadecimal increment, relative to the module's base address as shown in the memory map.

The regions for SRAM and peripherals include bit-band regions. Bit-banding provides atomic operations to bit data (see "Bit-Banding" on page 101).

The processor reserves regions of the Private peripheral bus (PPB) address range for core peripheral registers (see "Cortex-M4 Peripherals" on page 126).

Note: Within the memory map, all reserved space returns a bus fault when read or written.

Table 2-4. Memory Map

Start	End	Description	For details, see page						
Memory	Memory								
0x0000.0000	0x0003.FFFF	On-chip Flash	538						
0x0004.0000	0x00FF.FFFF	Reserved	-						
0x0100.0000	0x1FFF.FFFF	Reserved for ROM	524						
0x2000.0000	0x2000.7FFF	Bit-banded on-chip SRAM	523						
0x2000.8000	0x21FF.FFFF	Reserved	-						
0x2200.0000	0x220F.FFFF	Bit-band alias of bit-banded on-chip SRAM starting at 0x2000.0000	523						
0x2210.0000	0x3FFF.FFFF	Reserved	-						
FiRM Peripherals		·							
0x4000.0000	0x4000.0FFF	Watchdog timer 0	777						
0x4000.1000	0x4000.1FFF	Watchdog timer 1	777						
0x4000.2000	0x4000.3FFF	Reserved	-						
0x4000.4000	0x4000.4FFF	GPIO Port A	659						
0x4000.5000	0x4000.5FFF	GPIO Port B	659						
0x4000.6000	0x4000.6FFF	GPIO Port C	659						

Table 2-4. Memory Map (continued)

Start	End	Description	For details, see page
0x4000.7000	0x4000.7FFF	GPIO Port D	659
0x4000.8000	0x4000.8FFF	SSIO	973
0x4000.9000	0x4000.9FFF	SSI1	973
0x4000.A000	0x4000.AFFF	SSI2	973
0x4000.B000	0x4000.BFFF	SSI3	973
0x4000.C000	0x4000.CFFF	UART0	910
0x4000.D000	0x4000.DFFF	UART1	910
0x4000.E000	0x4000.EFFF	UART2	910
0x4000.F000	0x4000.FFFF	UART3	910
0x4001.0000	0x4001.0FFF	UART4	910
0x4001.1000	0x4001.1FFF	UART5	910
0x4001.2000	0x4001.2FFF	UART6	910
0x4001.3000	0x4001.3FFF	UART7	910
0x4001.4000	0x4001.FFFF	Reserved	-
Peripherals			
0x4002.0000	0x4002.0FFF	l ² C 0	1023
0x4002.1000	0x4002.1FFF	I ² C 1	1023
0x4002.2000	0x4002.2FFF	l ² C 2	1023
0x4002.3000	0x4002.3FFF	I ² C 3	1023
0x4002.4000	0x4002.4FFF	GPIO Port E	659
0x4002.5000	0x4002.5FFF	GPIO Port F	659
0x4002.6000	0x4002.6FFF	GPIO Port G	659
0x4002.7000	0x4002.7FFF	GPIO Port H	659
0x4002.8000	0x4002.8FFF	PWM 0	1248
0x4002.9000	0x4002.9FFF	PWM 1	1248
0x4002.A000	0x4002.BFFF	Reserved	-
0x4002.C000	0x4002.CFFF	QEI0	1318
0x4002.D000	0x4002.DFFF	QEI1	1318
0x4002.E000	0x4002.FFFF	Reserved	-
0x4003.0000	0x4003.0FFF	16/32-bit Timer 0	726
0x4003.1000	0x4003.1FFF	16/32-bit Timer 1	726
0x4003.2000	0x4003.2FFF	16/32-bit Timer 2	726
0x4003.3000	0x4003.3FFF	16/32-bit Timer 3	726
0x4003.4000	0x4003.4FFF	16/32-bit Timer 4	726
0x4003.5000	0x4003.5FFF	16/32-bit Timer 5	726
0x4003.6000	0x4003.6FFF	32/64-bit Timer 0	726
0x4003.7000	0x4003.7FFF	32/64-bit Timer 1	726
0x4003.8000	0x4003.8FFF	ADC0	820
0x4003.9000	0x4003.9FFF	ADC1	820
0x4003.A000	0x4003.BFFF	Reserved	-
0x4003.C000	0x4003.CFFF	Analog Comparators	1219

Table 2-4. Memory Map (continued)

Start	End	Description	For details, see page
0x4003.D000	0x4003.DFFF	GPIO Port J	659
0x4003.E000	0x4003.FFFF	Reserved	-
0x4004.0000	0x4004.0FFF	CAN0 Controller	1073
0x4004.1000	0x4004.1FFF	CAN1 Controller	1073
0x4004.2000	0x4004.BFFF	Reserved	-
0x4004.C000	0x4004.CFFF	32/64-bit Timer 2	726
0x4004.D000	0x4004.DFFF	32/64-bit Timer 3	726
0x4004.E000	0x4004.EFFF	32/64-bit Timer 4	726
0x4004.F000	0x4004.FFFF	32/64-bit Timer 5	726
0x4005.0000	0x4005.0FFF	USB	1125
0x4005.1000	0x4005.7FFF	Reserved	-
0x4005.8000	0x4005.8FFF	GPIO Port A (AHB aperture)	659
0x4005.9000	0x4005.9FFF	GPIO Port B (AHB aperture)	659
0x4005.A000	0x4005.AFFF	GPIO Port C (AHB aperture)	659
0x4005.B000	0x4005.BFFF	GPIO Port D (AHB aperture)	659
0x4005.C000	0x4005.CFFF	GPIO Port E (AHB aperture)	659
0x4005.D000	0x4005.DFFF	GPIO Port F (AHB aperture)	659
0x4005.E000	0x4005.EFFF	GPIO Port G (AHB aperture)	659
0x4005.F000	0x4005.FFFF	GPIO Port H (AHB aperture)	659
0x4006.0000	0x4006.0FFF	GPIO Port J (AHB aperture)	659
0x4006.1000	0x4006.1FFF	GPIO Port K (AHB aperture)	659
0x4006.2000	0x400A.EFFF	Reserved	-
0x400A.F000	0x400A.FFFF	EEPROM and Key Locker	556
0x400B.0000	0x400B.FFFF	Reserved	-
0x400C.0000	0x400C.0FFF	I ² C 4	1023
0x400C.1000	0x400C.1FFF	I ² C 5	1023
0x400C.2000	0x400F.8FFF	Reserved	-
0x400F.9000	0x400F.9FFF	System Exception Module	483
0x400F.A000	0x400F.BFFF	Reserved	-
0x400F.C000	0x400F.CFFF	Hibernation Module	504
0x400F.D000	0x400F.DFFF	Flash memory control	538
0x400F.E000	0x400F.EFFF	System control	239
0x400F.F000	0x400F.FFFF	μDMA	603
0x4010.0000	0x41FF.FFFF	Reserved	-
0x4200.0000	0x43FF.FFFF	Bit-banded alias of 0x4000.0000 through 0x400F.FFFF	-
0x4400.0000	0xDFFF.FFFF	Reserved	-
Private Peripheral Bus	•		
0xE000.0000	0xE000.0FFF	Instrumentation Trace Macrocell (ITM)	75
0xE000.1000	0xE000.1FFF	Data Watchpoint and Trace (DWT)	75
0xE000.2000	0xE000.2FFF	Flash Patch and Breakpoint (FPB)	75
0xE000.3000	0xE000.DFFF	Reserved	-

Table 2-4. Memory Map (continued)

Start	End	•	For details, see page
0xE000.E000	0xE000.EFFF	Cortex-M4F Peripherals (SysTick, NVIC, MPU, FPU and SCB)	138
0xE000.F000	0xE003.FFFF	Reserved	-
0xE004.0000	0xE004.0FFF	Trace Port Interface Unit (TPIU)	76
0xE004.1000	0xE004.1FFF	Embedded Trace Macrocell (ETM)	75
0xE004.2000	0xFFFF.FFFF	Reserved	-

2.4.1 Memory Regions, Types and Attributes

The memory map and the programming of the MPU split the memory map into regions. Each region has a defined memory type, and some regions have additional memory attributes. The memory type and attributes determine the behavior of accesses to the region.

The memory types are:

- Normal: The processor can re-order transactions for efficiency and perform speculative reads.
- Device: The processor preserves transaction order relative to other transactions to Device or Strongly Ordered memory.
- Strongly Ordered: The processor preserves transaction order relative to all other transactions.

The different ordering requirements for Device and Strongly Ordered memory mean that the memory system can buffer a write to Device memory but must not buffer a write to Strongly Ordered memory.

An additional memory attribute is Execute Never (XN), which means the processor prevents instruction accesses. A fault exception is generated only on execution of an instruction executed from an XN region.

2.4.2 Memory System Ordering of Memory Accesses

For most memory accesses caused by explicit memory access instructions, the memory system does not guarantee that the order in which the accesses complete matches the program order of the instructions, providing the order does not affect the behavior of the instruction sequence. Normally, if correct program execution depends on two memory accesses completing in program order, software must insert a memory barrier instruction between the memory access instructions (see "Software Ordering of Memory Accesses" on page 100).

However, the memory system does guarantee ordering of accesses to Device and Strongly Ordered memory. For two memory access instructions A1 and A2, if both A1 and A2 are accesses to either Device or Strongly Ordered memory, and if A1 occurs before A2 in program order, A1 is always observed before A2.

2.4.3 Behavior of Memory Accesses

Table 2-5 on page 100 shows the behavior of accesses to each region in the memory map. See "Memory Regions, Types and Attributes" on page 99 for more information on memory types and the XN attribute. Stellaris devices may have reserved memory areas within the address ranges shown below (refer to Table 2-4 on page 96 for more information).

Table 2-5. Memory Access Behavior

Address Range	Memory Region	Memory Type	Execute Never (XN)	Description
0x0000.0000 - 0x1FFF.FFFF	Code	Normal	-	This executable region is for program code. Data can also be stored here.
0x2000.0000 - 0x3FFF.FFFF	SRAM	Normal	-	This executable region is for data. Code can also be stored here. This region includes bit band and bit band alias areas (see Table 2-6 on page 102).
0x4000.0000 - 0x5FFF.FFFF	Peripheral	Device	XN	This region includes bit band and bit band alias areas (see Table 2-7 on page 102).
0x6000.0000 - 0x9FFF.FFFF	External RAM	Normal	-	This executable region is for data.
0xA000.0000 - 0xDFFF.FFFF	External device	Device	XN	This region is for external device memory.
0xE000.0000- 0xE00F.FFFF	Private peripheral bus	Strongly Ordered	XN	This region includes the NVIC, system timer, and system control block.
0xE010.0000- 0xFFFF.FFFF	Reserved	-	-	-

The Code, SRAM, and external RAM regions can hold programs. However, it is recommended that programs always use the Code region because the Cortex-M4F has separate buses that can perform instruction fetches and data accesses simultaneously.

The MPU can override the default memory access behavior described in this section. For more information, see "Memory Protection Unit (MPU)" on page 129.

The Cortex-M4F prefetches instructions ahead of execution and speculatively prefetches from branch target addresses.

2.4.4 Software Ordering of Memory Accesses

The order of instructions in the program flow does not always guarantee the order of the corresponding memory transactions for the following reasons:

- The processor can reorder some memory accesses to improve efficiency, providing this does not affect the behavior of the instruction sequence.
- The processor has multiple bus interfaces.
- Memory or devices in the memory map have different wait states.
- Some memory accesses are buffered or speculative.

"Memory System Ordering of Memory Accesses" on page 99 describes the cases where the memory system guarantees the order of memory accesses. Otherwise, if the order of memory accesses is critical, software must include memory barrier instructions to force that ordering. The Cortex-M4F has the following memory barrier instructions:

- The Data Memory Barrier (DMB) instruction ensures that outstanding memory transactions complete before subsequent memory transactions.
- The Data Synchronization Barrier (DSB) instruction ensures that outstanding memory transactions complete before subsequent instructions execute.
- The Instruction Synchronization Barrier (ISB) instruction ensures that the effect of all completed memory transactions is recognizable by subsequent instructions.

Memory barrier instructions can be used in the following situations:

MPU programming

- If the MPU settings are changed and the change must be effective on the very next instruction, use a DSB instruction to ensure the effect of the MPU takes place immediately at the end of context switching.
- Use an ISB instruction to ensure the new MPU setting takes effect immediately after programming the MPU region or regions, if the MPU configuration code was accessed using a branch or call. If the MPU configuration code is entered using exception mechanisms, then an ISB instruction is not required.

Vector table

If the program changes an entry in the vector table and then enables the corresponding exception, use a DMB instruction between the operations. The DMB instruction ensures that if the exception is taken immediately after being enabled, the processor uses the new exception vector.

Self-modifying code

If a program contains self-modifying code, use an ISB instruction immediately after the code modification in the program. The ISB instruction ensures subsequent instruction execution uses the updated program.

Memory map switching

If the system contains a memory map switching mechanism, use a \mbox{DSB} instruction after switching the memory map in the program. The \mbox{DSB} instruction ensures subsequent instruction execution uses the updated memory map.

Dynamic exception priority change

When an exception priority has to change when the exception is pending or active, use DSB instructions after the change. The change then takes effect on completion of the DSB instruction.

Memory accesses to Strongly Ordered memory, such as the System Control Block, do not require the use of DMB instructions.

For more information on the memory barrier instructions, see the *Cortex*™-*M3/M4 Instruction Set Technical User's Manual.*

2.4.5 Bit-Banding

A bit-band region maps each word in a bit-band alias region to a single bit in the bit-band region. The bit-band regions occupy the lowest 1 MB of the SRAM and peripheral memory regions. Accesses to the 32-MB SRAM alias region map to the 1-MB SRAM bit-band region, as shown in Table 2-6 on page 102. Accesses to the 32-MB peripheral alias region map to the 1-MB peripheral bit-band region, as shown in Table 2-7 on page 102. For the specific address range of the bit-band regions, see Table 2-4 on page 96.

Note: A word access to the SRAM or the peripheral bit-band alias region maps to a single bit in the SRAM or peripheral bit-band region.

A word access to a bit band address results in a word access to the underlying memory, and similarly for halfword and byte accesses. This allows bit band accesses to match the access requirements of the underlying peripheral.

Table 2-6. SRAM Memory Bit-Banding Regions

Address Range		Memory Region	Instruction and Data Accesses		
Start	End	Memory Region	instruction and Data Accesses		
0x2000.0000	0x2000.7FFF	SRAM bit-band region	Direct accesses to this memory range behave as SRAM memory accesses, but this region is also bit addressable through bit-band alias.		
0x2200.0000	0x220F.FFFF	SRAM bit-band alias	Data accesses to this region are remapped to bit band region. A write operation is performed as read-modify-write. Instruction accesses are not remapped.		

Table 2-7. Peripheral Memory Bit-Banding Regions

Address Range		Memory Region	Instruction and Data Accesses		
Start	End	Welliory Region	Instruction and Data Accesses		
0x4000.0000	0x400F.FFFF	Peripheral bit-band region	Direct accesses to this memory range behave as peripheral memory accesses, but this region is also bit addressable through bit-band alias.		
0x4200.0000	0x43FF.FFFF	,	Data accesses to this region are remapped to bit band region. A write operation is performed as read-modify-write. Instruction accesses are not permitted.		

The following formula shows how the alias region maps onto the bit-band region:

```
bit_word_offset = (byte_offset x 32) + (bit_number x 4)
bit_word_addr = bit_band_base + bit_word_offset
```

bit word offset

where:

The position of the target bit in the bit-band memory region.

bit_word_addr

The address of the word in the alias memory region that maps to the targeted bit.

bit_band_base

The starting address of the alias region.

byte offset

The number of the byte in the bit-band region that contains the targeted bit.

bit number

The bit position, 0-7, of the targeted bit.

Figure 2-4 on page 103 shows examples of bit-band mapping between the SRAM bit-band alias region and the SRAM bit-band region:

■ The alias word at 0x23FF.FFE0 maps to bit 0 of the bit-band byte at 0x200F.FFFF:

```
0x23FF.FFE0 = 0x2200.0000 + (0x000F.FFFF*32) + (0*4)
```

■ The alias word at 0x23FF.FFFC maps to bit 7 of the bit-band byte at 0x200F.FFFF:

```
0x23FF.FFFC = 0x2200.0000 + (0x000F.FFFF*32) + (7*4)
```


■ The alias word at 0x2200.0000 maps to bit 0 of the bit-band byte at 0x2000.0000:

```
0x2200.0000 = 0x2200.0000 + (0*32) + (0*4)
```

■ The alias word at 0x2200.001C maps to bit 7 of the bit-band byte at 0x2000.0000:

```
0x2200.001C = 0x2200.0000 + (0*32) + (7*4)
```

Figure 2-4. Bit-Band Mapping



2.4.5.1 Directly Accessing an Alias Region

Writing to a word in the alias region updates a single bit in the bit-band region.

Bit 0 of the value written to a word in the alias region determines the value written to the targeted bit in the bit-band region. Writing a value with bit 0 set writes a 1 to the bit-band bit, and writing a value with bit 0 clear writes a 0 to the bit-band bit.

Bits 31:1 of the alias word have no effect on the bit-band bit. Writing 0x01 has the same effect as writing 0xFF. Writing 0x00 has the same effect as writing 0x0E.

When reading a word in the alias region, 0x0000.0000 indicates that the targeted bit in the bit-band region is clear and 0x0000.0001 indicates that the targeted bit in the bit-band region is set.

2.4.5.2 Directly Accessing a Bit-Band Region


"Behavior of Memory Accesses" on page 99 describes the behavior of direct byte, halfword, or word accesses to the bit-band regions.

2.4.6 Data Storage

The processor views memory as a linear collection of bytes numbered in ascending order from zero. For example, bytes 0-3 hold the first stored word, and bytes 4-7 hold the second stored word. Data is stored in little-endian format, with the least-significant byte (lsbyte) of a word stored at the

lowest-numbered byte, and the most-significant byte (msbyte) stored at the highest-numbered byte. Figure 2-5 on page 104 illustrates how data is stored.

Figure 2-5. Data Storage



2.4.7 Synchronization Primitives

The Cortex-M4F instruction set includes pairs of synchronization primitives which provide a non-blocking mechanism that a thread or process can use to obtain exclusive access to a memory location. Software can use these primitives to perform a guaranteed read-modify-write memory update sequence or for a semaphore mechanism.

A pair of synchronization primitives consists of:

- A Load-Exclusive instruction, which is used to read the value of a memory location and requests exclusive access to that location.
- A Store-Exclusive instruction, which is used to attempt to write to the same memory location and returns a status bit to a register. If this status bit is clear, it indicates that the thread or process gained exclusive access to the memory and the write succeeds; if this status bit is set, it indicates that the thread or process did not gain exclusive access to the memory and no write was performed.

The pairs of Load-Exclusive and Store-Exclusive instructions are:

- The word instructions LDREX and STREX
- The halfword instructions LDREXH and STREXH
- The byte instructions LDREXB and STREXB

Software must use a Load-Exclusive instruction with the corresponding Store-Exclusive instruction.

To perform an exclusive read-modify-write of a memory location, software must:

- **1.** Use a Load-Exclusive instruction to read the value of the location.
- **2.** Modify the value, as required.
- 3. Use a Store-Exclusive instruction to attempt to write the new value back to the memory location.
- 4. Test the returned status bit.

If the status bit is clear, the read-modify-write completed successfully. If the status bit is set, no write was performed, which indicates that the value returned at step 1 might be out of date. The software must retry the entire read-modify-write sequence.

Software can use the synchronization primitives to implement a semaphore as follows:

- 1. Use a Load-Exclusive instruction to read from the semaphore address to check whether the semaphore is free.
- 2. If the semaphore is free, use a Store-Exclusive to write the claim value to the semaphore address.
- **3.** If the returned status bit from step 2 indicates that the Store-Exclusive succeeded, then the software has claimed the semaphore. However, if the Store-Exclusive failed, another process might have claimed the semaphore after the software performed step 1.

The Cortex-M4F includes an exclusive access monitor that tags the fact that the processor has executed a Load-Exclusive instruction. The processor removes its exclusive access tag if:

- It executes a CLREX instruction.
- It executes a Store-Exclusive instruction, regardless of whether the write succeeds.
- An exception occurs, which means the processor can resolve semaphore conflicts between different threads.

For more information about the synchronization primitive instructions, see the *Cortex™-M3/M4 Instruction Set Technical User's Manual.*

2.5 Exception Model

The ARM Cortex-M4F processor and the Nested Vectored Interrupt Controller (NVIC) prioritize and handle all exceptions in Handler Mode. The processor state is automatically stored to the stack on an exception and automatically restored from the stack at the end of the Interrupt Service Routine (ISR). The vector is fetched in parallel to the state saving, enabling efficient interrupt entry. The processor supports tail-chaining, which enables back-to-back interrupts to be performed without the overhead of state saving and restoration.

Table 2-8 on page 107 lists all exception types. Software can set eight priority levels on seven of these exceptions (system handlers) as well as on 85 interrupts (listed in Table 2-9 on page 108).

Priorities on the system handlers are set with the NVIC **System Handler Priority n (SYSPRIn)** registers. Interrupts are enabled through the NVIC **Interrupt Set Enable n (ENn)** register and prioritized with the NVIC **Interrupt Priority n (PRIn)** registers. Priorities can be grouped by splitting priority levels into preemption priorities and subpriorities. All the interrupt registers are described in "Nested Vectored Interrupt Controller (NVIC)" on page 128.

Internally, the highest user-programmable priority (0) is treated as fourth priority, after a Reset, Non-Maskable Interrupt (NMI), and a Hard Fault, in that order. Note that 0 is the default priority for all the programmable priorities.

Important: After a write to clear an interrupt source, it may take several processor cycles for the NVIC to see the interrupt source de-assert. Thus if the interrupt clear is done as the last action in an interrupt handler, it is possible for the interrupt handler to complete while the NVIC sees the interrupt as still asserted, causing the interrupt handler to be

re-entered errantly. This situation can be avoided by either clearing the interrupt source at the beginning of the interrupt handler or by performing a read or write after the write to clear the interrupt source (and flush the write buffer).

See "Nested Vectored Interrupt Controller (NVIC)" on page 128 for more information on exceptions and interrupts.

2.5.1 Exception States

Each exception is in one of the following states:

- Inactive. The exception is not active and not pending.
- **Pending.** The exception is waiting to be serviced by the processor. An interrupt request from a peripheral or from software can change the state of the corresponding interrupt to pending.
- Active. An exception that is being serviced by the processor but has not completed.

Note: An exception handler can interrupt the execution of another exception handler. In this case, both exceptions are in the active state.

■ **Active and Pending.** The exception is being serviced by the processor, and there is a pending exception from the same source.

2.5.2 Exception Types

The exception types are:

- Reset. Reset is invoked on power up or a warm reset. The exception model treats reset as a special form of exception. When reset is asserted, the operation of the processor stops, potentially at any point in an instruction. When reset is deasserted, execution restarts from the address provided by the reset entry in the vector table. Execution restarts as privileged execution in Thread mode.
- NMI. A non-maskable Interrupt (NMI) can be signaled using the NMI signal or triggered by software using the Interrupt Control and State (INTCTRL) register. This exception has the highest priority other than reset. NMI is permanently enabled and has a fixed priority of -2. NMIs cannot be masked or prevented from activation by any other exception or preempted by any exception other than reset.
- Hard Fault. A hard fault is an exception that occurs because of an error during exception processing, or because an exception cannot be managed by any other exception mechanism. Hard faults have a fixed priority of -1, meaning they have higher priority than any exception with configurable priority.
- Memory Management Fault. A memory management fault is an exception that occurs because of a memory protection related fault, including access violation and no match. The MPU or the fixed memory protection constraints determine this fault, for both instruction and data memory transactions. This fault is used to abort instruction accesses to Execute Never (XN) memory regions, even if the MPU is disabled.
- **Bus Fault.** A bus fault is an exception that occurs because of a memory-related fault for an instruction or data memory transaction such as a prefetch fault or a memory access fault. This fault can be enabled or disabled.

- **Usage Fault.** A usage fault is an exception that occurs because of a fault related to instruction execution, such as:
 - An undefined instruction
 - An illegal unaligned access
 - Invalid state on instruction execution
 - An error on exception return

An unaligned address on a word or halfword memory access or division by zero can cause a usage fault when the core is properly configured.

- **SVCall.** A supervisor call (SVC) is an exception that is triggered by the SVC instruction. In an OS environment, applications can use SVC instructions to access OS kernel functions and device drivers.
- **Debug Monitor.** This exception is caused by the debug monitor (when not halting). This exception is only active when enabled. This exception does not activate if it is a lower priority than the current activation.
- **PendSV.** PendSV is a pendable, interrupt-driven request for system-level service. In an OS environment, use PendSV for context switching when no other exception is active. PendSV is triggered using the **Interrupt Control and State (INTCTRL)** register.
- SysTick. A SysTick exception is an exception that the system timer generates when it reaches zero when it is enabled to generate an interrupt. Software can also generate a SysTick exception using the Interrupt Control and State (INTCTRL) register. In an OS environment, the processor can use this exception as system tick.
- Interrupt (IRQ). An interrupt, or IRQ, is an exception signaled by a peripheral or generated by a software request and fed through the NVIC (prioritized). All interrupts are asynchronous to instruction execution. In the system, peripherals use interrupts to communicate with the processor. Table 2-9 on page 108 lists the interrupts on the LM4F232H5QC controller.

For an asynchronous exception, other than reset, the processor can execute another instruction between when the exception is triggered and when the processor enters the exception handler.

Privileged software can disable the exceptions that Table 2-8 on page 107 shows as having configurable priority (see the **SYSHNDCTRL** register on page 177 and the **DIS0** register on page 148).

For more information about hard faults, memory management faults, bus faults, and usage faults, see "Fault Handling" on page 115.

Table 2-8. Exception Types

Exception Type	Vector Number	Priority ^a	Vector Address or Offset ^b	Activation
-	0	-	0x0000.0000	Stack top is loaded from the first entry of the vector table on reset.
Reset	1	-3 (highest)	0x0000.0004	Asynchronous
Non-Maskable Interrupt (NMI)	2	-2	0x0000.0008	Asynchronous
Hard Fault	3	-1	0x0000.000C	-
Memory Management	4	programmable ^c	0x0000.0010	Synchronous

Table 2-8. Exception Types (continued)

Exception Type	Vector Number	Priority ^a	Vector Address or Offset ^b	Activation
Bus Fault	5	programmable ^c	0x0000.0014	Synchronous when precise and asynchronous when imprecise
Usage Fault	6	programmable ^c	0x0000.0018	Synchronous
-	7-10	-	-	Reserved
SVCall	11	programmable ^c	0x0000.002C	Synchronous
Debug Monitor	12	programmable ^c	0x0000.0030	Synchronous
-	13	-	-	Reserved
PendSV	14	programmable ^c	0x0000.0038	Asynchronous
SysTick	15	programmable ^c	0x0000.003C	Asynchronous
Interrupts	16 and above	programmable ^d	0x0000.0040 and above	Asynchronous

a. 0 is the default priority for all the programmable priorities.

Table 2-9. Interrupts

Vector Number	Interrupt Number (Bit in Interrupt Registers)	Vector Address or Offset	Description
0-15	-	0x0000.0000 - 0x0000.003C	Processor exceptions
16	0	0x0000.0040	GPIO Port A
17	1	0x0000.0044	GPIO Port B
18	2	0x0000.0048	GPIO Port C
19	3	0x0000.004C	GPIO Port D
20	4	0x0000.0050	GPIO Port E
21	5	0x0000.0054	UART0
22	6	0x0000.0058	UART1
23	7	0x0000.005C	SSI0
24	8	0x0000.0060	I ² C0
25	9	0x0000.0064	PWM0 Fault
26	10	0x0000.0068	PWM0 Generator 0
27	11	0x0000.006C	PWM0 Generator 1
28	12	0x0000.0070	PWM0 Generator 2
29	13	0x0000.0074	QEI0
30	14	0x0000.0078	ADC0 Sequence 0
31	15	0x0000.007C	ADC0 Sequence 1
32	16	0x0000.0080	ADC0 Sequence 2
33	17	0x0000.0084	ADC0 Sequence 3
34	18	0x0000.0088	Watchdog Timers 0 and 1
35	19	0x0000.008C	16/32-Bit Timer 0A
36	20	0x0000.0090	16/32-Bit Timer 0B
37	21	0x0000.0094	16/32-Bit Timer 1A

b. See "Vector Table" on page 111.

c. See SYSPRI1 on page 174.

d. See PRIn registers on page 156.

Table 2-9. Interrupts (continued)

Vector Number	Interrupt Number (Bit in Interrupt Registers)	Vector Address or Offset	Description
38	22	0x0000.0098	16/32-Bit Timer 1B
39	23	0x0000.009C	16/32-Bit Timer 2A
40	24	0x0000.00A0	16/32-Bit Timer 2B
41	25	0x0000.00A4	Analog Comparator 0
42	26	0x0000.00A8	Analog Comparator 1
43	27	0x0000.00AC	Analog Comparator 2
44	28	0x0000.00B0	System Control
45	29	0x0000.00B4	Flash Memory Control and EEPROM Control
46	30	0x0000.00B8	GPIO Port F
47	31	0x0000.00BC	GPIO Port G
48	32	0x0000.00C0	GPIO Port H
49	33	0x0000.00C4	UART2
50	34	0x0000.00C8	SSI1
51	35	0x0000.00CC	16/32-Bit Timer 3A
52	36	0x0000.00D0	16/32-Bit Timer 3B
53	37	0x0000.00D4	I ² C1
54	38	0x0000.00D8	QEI1
55	39	0x0000.00DC	CAN0
56	40	0x0000.00E0	CAN1
57-58	41-42	-	Reserved
59	43	0x0000.00EC	Hibernation Module
60	44	0x0000.00F0	USB
61	45	0x0000.00F4	PWM Generator 3
62	46	0x0000.00F8	μDMA Software
63	47	0x0000.00FC	μDMA Error
64	48	0x0000.0100	ADC1 Sequence 0
65	49	0x0000.0104	ADC1 Sequence 1
66	50	0x0000.0108	ADC1 Sequence 2
67	51	0x0000.010C	ADC1 Sequence 3
68-69	52-53	-	Reserved
70	54	0x0000.0118	GPIO Port J
71	55	0x0000.011C	GPIO Port K
72	56	-	Reserved
73	57	0x0000.0124	SSI2
74	58	0x0000.0128	SSI3
75	59	0x0000.012C	UART3
76	60	0x0000.0130	UART4
77	61	0x0000.0134	UART5
78	62	0x0000.0138	UART6
79	63	0x0000.013C	UART7

Table 2-9. Interrupts (continued)

Vector Number	Interrupt Number (Bit in Interrupt Registers)	Vector Address or Offset	Description
80-83	64-67	0x0000.0140 - 0x0000.014C	Reserved
84	68	0x0000.0150	l ² C2
85	69	0x0000.0154	I ² C3
86	70	0x0000.0158	16/32-Bit Timer 4A
87	71	0x0000.015C	16/32-Bit Timer 4B
88-107	72-91	0x0000.0160 - 0x0000.01AC	Reserved
108	92	0x0000.01B0	16/32-Bit Timer 5A
109	93	0x0000.01B4	16/32-Bit Timer 5B
110	94	0x0000.01B8	32/64-Bit Timer 0A
111	95	0x0000.01BC	32/64-Bit Timer 0B
112	96	0x0000.01C0	32/64-Bit Timer 1A
113	97	0x0000.01C4	32/64-Bit Timer 1B
114	98	0x0000.01C8	32/64-Bit Timer 2A
115	99	0x0000.01CC	32/64-Bit Timer 2B
116	100	0x0000.01D0	32/64-Bit Timer 3A
117	101	0x0000.01D4	32/64-Bit Timer 3B
118	102	0x0000.01D8	32/64-Bit Timer 4A
119	103	0x0000.01DC	32/64-Bit Timer 4B
120	104	0x0000.01E0	32/64-Bit Timer 5A
121	105	0x0000.01E4	32/64-Bit Timer 5B
122	106	0x0000.01E8	System Exception (imprecise)
123-124	107-108	-	Reserved
125	109	0x0000.01F4	l ² C4
126	110	0x0000.01F8	l ² C5
127-149	111-133	-	Reserved
150	134	0x0000.0258	PWM1 Generator 0
151	135	0x0000.025C	PWM1 Generator 1
152	136	0x0000.0260	PWM1 Generator 2
153	137	0x0000.0264	PWM1 Generator 3
154	138	0x0000.0268	PWM1 Fault

2.5.3 Exception Handlers


The processor handles exceptions using:

- Interrupt Service Routines (ISRs). Interrupts (IRQx) are the exceptions handled by ISRs.
- Fault Handlers. Hard fault, memory management fault, usage fault, and bus fault are fault exceptions handled by the fault handlers.
- **System Handlers.** NMI, PendSV, SVCall, SysTick, and the fault exceptions are all system exceptions that are handled by system handlers.

2.5.4 Vector Table

The vector table contains the reset value of the stack pointer and the start addresses, also called exception vectors, for all exception handlers. The vector table is constructed using the vector address or offset shown in Table 2-8 on page 107. Figure 2-6 on page 111 shows the order of the exception vectors in the vector table. The least-significant bit of each vector must be 1, indicating that the exception handler is Thumb code

Figure 2-6. Vector Table



On system reset, the vector table is fixed at address 0x0000.0000. Privileged software can write to the **Vector Table Offset (VTABLE)** register to relocate the vector table start address to a different memory location, in the range 0x0000.0400 to 0x3FFF.FC00 (see "Vector Table" on page 111). Note that when configuring the **VTABLE** register, the offset must be aligned on a 1024-byte boundary.

2.5.5 Exception Priorities

As Table 2-8 on page 107 shows, all exceptions have an associated priority, with a lower priority value indicating a higher priority and configurable priorities for all exceptions except Reset, Hard fault, and NMI. If software does not configure any priorities, then all exceptions with a configurable priority have a priority of 0. For information about configuring exception priorities, see page 174 and page 156.

Note: Configurable priority values for the Stellaris implementation are in the range 0-7. This means that the Reset, Hard fault, and NMI exceptions, with fixed negative priority values, always have higher priority than any other exception.

For example, assigning a higher priority value to IRQ[0] and a lower priority value to IRQ[1] means that IRQ[1] has higher priority than IRQ[0]. If both IRQ[1] and IRQ[0] are asserted, IRQ[1] is processed before IRQ[0].

If multiple pending exceptions have the same priority, the pending exception with the lowest exception number takes precedence. For example, if both IRQ[0] and IRQ[1] are pending and have the same priority, then IRQ[0] is processed before IRQ[1].

When the processor is executing an exception handler, the exception handler is preempted if a higher priority exception occurs. If an exception occurs with the same priority as the exception being handled, the handler is not preempted, irrespective of the exception number. However, the status of the new interrupt changes to pending.

2.5.6 Interrupt Priority Grouping

To increase priority control in systems with interrupts, the NVIC supports priority grouping. This grouping divides each interrupt priority register entry into two fields:

- An upper field that defines the group priority
- A lower field that defines a subpriority within the group

Only the group priority determines preemption of interrupt exceptions. When the processor is executing an interrupt exception handler, another interrupt with the same group priority as the interrupt being handled does not preempt the handler.

If multiple pending interrupts have the same group priority, the subpriority field determines the order in which they are processed. If multiple pending interrupts have the same group priority and subpriority, the interrupt with the lowest IRQ number is processed first.

For information about splitting the interrupt priority fields into group priority and subpriority, see page 168.

2.5.7 Exception Entry and Return

Descriptions of exception handling use the following terms:

- **Preemption.** When the processor is executing an exception handler, an exception can preempt the exception handler if its priority is higher than the priority of the exception being handled. See "Interrupt Priority Grouping" on page 112 for more information about preemption by an interrupt. When one exception preempts another, the exceptions are called nested exceptions. See "Exception Entry" on page 113 more information.
- **Return.** Return occurs when the exception handler is completed, and there is no pending exception with sufficient priority to be serviced and the completed exception handler was not handling a late-arriving exception. The processor pops the stack and restores the processor state to the state it had before the interrupt occurred. See "Exception Return" on page 114 for more information.
- **Tail-Chaining.** This mechanism speeds up exception servicing. On completion of an exception handler, if there is a pending exception that meets the requirements for exception entry, the stack pop is skipped and control transfers to the new exception handler.

■ Late-Arriving. This mechanism speeds up preemption. If a higher priority exception occurs during state saving for a previous exception, the processor switches to handle the higher priority exception and initiates the vector fetch for that exception. State saving is not affected by late arrival because the state saved is the same for both exceptions. Therefore, the state saving continues uninterrupted. The processor can accept a late arriving exception until the first instruction of the exception handler of the original exception enters the execute stage of the processor. On return from the exception handler of the late-arriving exception, the normal tail-chaining rules apply.

2.5.7.1 Exception Entry

Exception entry occurs when there is a pending exception with sufficient priority and either the processor is in Thread mode or the new exception is of higher priority than the exception being handled, in which case the new exception preempts the original exception.

When one exception preempts another, the exceptions are nested.

Sufficient priority means the exception has more priority than any limits set by the mask registers (see **PRIMASK** on page 89, **FAULTMASK** on page 90, and **BASEPRI** on page 91). An exception with less priority than this is pending but is not handled by the processor.

When the processor takes an exception, unless the exception is a tail-chained or a late-arriving exception, the processor pushes information onto the current stack. This operation is referred to as *stacking* and the structure of eight data words is referred to as *stack frame*.

When using floating-point routines, the Cortex-M4F processor automatically stacks the architected floating-point state on exception entry. Figure 2-7 on page 114 shows the Cortex-M4F stack frame layout when floating-point state is preserved on the stack as the result of an interrupt or an exception.

Note: Where stack space for floating-point state is not allocated, the stack frame is the same as that of ARMv7-M implementations without an FPU. Figure 2-7 on page 114 shows this stack frame also.




Figure 2-7. Exception Stack Frame

Immediately after stacking, the stack pointer indicates the lowest address in the stack frame.

The stack frame includes the return address, which is the address of the next instruction in the interrupted program. This value is restored to the **PC** at exception return so that the interrupted program resumes.

In parallel to the stacking operation, the processor performs a vector fetch that reads the exception handler start address from the vector table. When stacking is complete, the processor starts executing the exception handler. At the same time, the processor writes an EXC_RETURN value to the **LR**, indicating which stack pointer corresponds to the stack frame and what operation mode the processor was in before the entry occurred.

If no higher-priority exception occurs during exception entry, the processor starts executing the exception handler and automatically changes the status of the corresponding pending interrupt to active.

If another higher-priority exception occurs during exception entry, known as late arrival, the processor starts executing the exception handler for this exception and does not change the pending status of the earlier exception.

2.5.7.2 Exception Return

Exception return occurs when the processor is in Handler mode and executes one of the following instructions to load the EXC_RETURN value into the **PC**:

- An LDM or POP instruction that loads the PC
- A BX instruction using any register
- An LDR instruction with the PC as the destination

EXC_RETURN is the value loaded into the **LR** on exception entry. The exception mechanism relies on this value to detect when the processor has completed an exception handler. The lowest five bits of this value provide information on the return stack and processor mode. Table 2-10 on page 115 shows the EXC_RETURN values with a description of the exception return behavior.

EXC_RETURN bits 31:5 are all set. When this value is loaded into the **PC**, it indicates to the processor that the exception is complete, and the processor initiates the appropriate exception return sequence.

Table 2-10. Exception Return Behavior

EXC_RETURN[31:0]	Description
0xFFFF.FFE0	Reserved
0xFFFF.FFE1	Return to Handler mode.
	Exception return uses floating-point state from MSP.
	Execution uses MSP after return.
0xFFFF.FFE2 - 0xFFFF.FFE8	Reserved
0xFFFF.FFE9	Return to Thread mode.
	Exception return uses floating-point state from MSP.
	Execution uses MSP after return.
0xFFFF.FFEA - 0xFFFF.FFEC	Reserved
0xFFFF.FFED	Return to Thread mode.
	Exception return uses floating-point state from PSP.
	Execution uses PSP after return.
0xFFFF.FFEE - 0xFFFF.FFF0	Reserved
0xFFFF.FFF1	Return to Handler mode.
	Exception return uses non-floating-point state from MSP.
	Execution uses MSP after return.
0xFFFF.FFF2 - 0xFFFF.FFF8	Reserved
0xFFFF.FFF9	Return to Thread mode.
	Exception return uses non-floating-point state from MSP.
	Execution uses MSP after return.
0xFFFF.FFFA - 0xFFFF.FFFC	Reserved
0xFFFF.FFFD	Return to Thread mode.
	Exception return uses non-floating-point state from PSP.
	Execution uses PSP after return.
0xFFFF.FFFE - 0xFFFF.FFFF	Reserved

2.6 Fault Handling

Faults are a subset of the exceptions (see "Exception Model" on page 105). The following conditions generate a fault:

■ A bus error on an instruction fetch or vector table load or a data access.

- An internally detected error such as an undefined instruction or an attempt to change state with a BX instruction.
- Attempting to execute an instruction from a memory region marked as Non-Executable (XN).
- An MPU fault because of a privilege violation or an attempt to access an unmanaged region.

2.6.1 Fault Types

Table 2-11 on page 116 shows the types of fault, the handler used for the fault, the corresponding fault status register, and the register bit that indicates the fault has occurred. See page 181 for more information about the fault status registers.

Table 2-11. Faults

Fault	Handler	Fault Status Register	Bit Name
Bus error on a vector read	Hard fault	Hard Fault Status (HFAULTSTAT)	VECT
Fault escalated to a hard fault	Hard fault	Hard Fault Status (HFAULTSTAT)	FORCED
MPU or default memory mismatch on instruction access	Memory management fault	Memory Management Fault Status (MFAULTSTAT)	IERR ^a
MPU or default memory mismatch on data access	Memory management fault	Memory Management Fault Status (MFAULTSTAT)	DERR
MPU or default memory mismatch on exception stacking	Memory management fault	Memory Management Fault Status (MFAULTSTAT)	MSTKE
MPU or default memory mismatch on exception unstacking	Memory management fault	Memory Management Fault Status (MFAULTSTAT)	MUSTKE
MPU or default memory mismatch during lazy floating-point state preservation	Memory management fault	Memory Management Fault Status (MFAULTSTAT)	MLSPERR
Bus error during exception stacking	Bus fault	Bus Fault Status (BFAULTSTAT)	BSTKE
Bus error during exception unstacking	Bus fault	Bus Fault Status (BFAULTSTAT)	BUSTKE
Bus error during instruction prefetch	Bus fault	Bus Fault Status (BFAULTSTAT)	IBUS
Bus error during lazy floating-point state preservation	Bus fault	Bus Fault Status (BFAULTSTAT)	BLSPE
Precise data bus error	Bus fault	Bus Fault Status (BFAULTSTAT)	PRECISE
Imprecise data bus error	Bus fault	Bus Fault Status (BFAULTSTAT)	IMPRE
Attempt to access a coprocessor	Usage fault	Usage Fault Status (UFAULTSTAT)	NOCP
Undefined instruction	Usage fault	Usage Fault Status (UFAULTSTAT)	UNDEF
Attempt to enter an invalid instruction set state ^b	Usage fault	Usage Fault Status (UFAULTSTAT)	INVSTAT
Invalid EXC_RETURN value	Usage fault	Usage Fault Status (UFAULTSTAT)	INVPC
Illegal unaligned load or store	Usage fault	Usage Fault Status (UFAULTSTAT)	UNALIGN
Divide by 0	Usage fault	Usage Fault Status (UFAULTSTAT)	DIV0

a. Occurs on an access to an XN region even if the MPU is disabled.

2.6.2 Fault Escalation and Hard Faults

All fault exceptions except for hard fault have configurable exception priority (see **SYSPRI1** on page 174). Software can disable execution of the handlers for these faults (see **SYSHNDCTRL** on page 177).

b. Attempting to use an instruction set other than the Thumb instruction set, or returning to a non load-store-multiple instruction with ICI continuation.

Usually, the exception priority, together with the values of the exception mask registers, determines whether the processor enters the fault handler, and whether a fault handler can preempt another fault handler as described in "Exception Model" on page 105.

In some situations, a fault with configurable priority is treated as a hard fault. This process is called priority escalation, and the fault is described as *escalated to hard fault*. Escalation to hard fault occurs when:

- A fault handler causes the same kind of fault as the one it is servicing. This escalation to hard fault occurs because a fault handler cannot preempt itself because it must have the same priority as the current priority level.
- A fault handler causes a fault with the same or lower priority as the fault it is servicing. This situation happens because the handler for the new fault cannot preempt the currently executing fault handler.
- An exception handler causes a fault for which the priority is the same as or lower than the currently executing exception.
- A fault occurs and the handler for that fault is not enabled.

If a bus fault occurs during a stack push when entering a bus fault handler, the bus fault does not escalate to a hard fault. Thus if a corrupted stack causes a fault, the fault handler executes even though the stack push for the handler failed. The fault handler operates but the stack contents are corrupted.

Note: Only Reset and NMI can preempt the fixed priority hard fault. A hard fault can preempt any exception other than Reset, NMI, or another hard fault.

2.6.3 Fault Status Registers and Fault Address Registers

The fault status registers indicate the cause of a fault. For bus faults and memory management faults, the fault address register indicates the address accessed by the operation that caused the fault, as shown in Table 2-12 on page 117.

Table 2-12. Fault Status and Fault Address Registers

Handler	Status Register Name	Address Register Name	Register Description
Hard fault	Hard Fault Status (HFAULTSTAT)	-	page 187
Memory management	Memory Management Fault Status	Memory Management Fault	page 181
fault	(MFAULTSTAT)	Address (MMADDR)	page 188
Bus fault	Bus Fault Status (BFAULTSTAT)	Bus Fault Address	page 181
		(FAULTADDR)	page 189
Usage fault	Usage Fault Status (UFAULTSTAT)	-	page 181

2.6.4 **Lockup**

The processor enters a lockup state if a hard fault occurs when executing the NMI or hard fault handlers. When the processor is in the lockup state, it does not execute any instructions. The processor remains in lockup state until it is reset, an NMI occurs, or it is halted by a debugger.

Note: If the lockup state occurs from the NMI handler, a subsequent NMI does not cause the processor to leave the lockup state.

2.7 Power Management

The Cortex-M4F processor sleep modes reduce power consumption:

- Sleep mode stops the processor clock.
- Deep-sleep mode stops the system clock and switches off the PLL and Flash memory.

The SLEEPDEEP bit of the **System Control (SYSCTRL)** register selects which sleep mode is used (see page 170). For more information about the behavior of the sleep modes, see "System Control" on page 231.

This section describes the mechanisms for entering sleep mode and the conditions for waking up from sleep mode, both of which apply to Sleep mode and Deep-sleep mode.

2.7.1 Entering Sleep Modes

This section describes the mechanisms software can use to put the processor into one of the sleep modes.

The system can generate spurious wake-up events, for example a debug operation wakes up the processor. Therefore, software must be able to put the processor back into sleep mode after such an event. A program might have an idle loop to put the processor back to sleep mode.

2.7.1.1 Wait for Interrupt

The wait for interrupt instruction, WFI, causes immediate entry to sleep mode unless the wake-up condition is true (see "Wake Up from WFI or Sleep-on-Exit" on page 119). When the processor executes a WFI instruction, it stops executing instructions and enters sleep mode. See the Cortex™-M3/M4 Instruction Set Technical User's Manual for more information.

2.7.1.2 Wait for Event

The wait for event instruction, WFE, causes entry to sleep mode conditional on the value of a one-bit event register. When the processor executes a WFE instruction, it checks the event register. If the register is 0, the processor stops executing instructions and enters sleep mode. If the register is 1, the processor clears the register and continues executing instructions without entering sleep mode.

If the event register is 1, the processor must not enter sleep mode on execution of a WFE instruction. Typically, this situation occurs if an SEV instruction has been executed. Software cannot access this register directly.

See the Cortex™-M3/M4 Instruction Set Technical User's Manual for more information.

2.7.1.3 Sleep-on-Exit

If the SLEEPEXIT bit of the **SYSCTRL** register is set, when the processor completes the execution of all exception handlers, it returns to Thread mode and immediately enters sleep mode. This mechanism can be used in applications that only require the processor to run when an exception occurs.

2.7.2 Wake Up from Sleep Mode

The conditions for the processor to wake up depend on the mechanism that cause it to enter sleep mode.

2.7.2.1 Wake Up from WFI or Sleep-on-Exit

Normally, the processor wakes up only when the NVIC detects an exception with sufficient priority to cause exception entry. Some embedded systems might have to execute system restore tasks after the processor wakes up and before executing an interrupt handler. Entry to the interrupt handler can be delayed by setting the PRIMASK bit and clearing the FAULTMASK bit. If an interrupt arrives that is enabled and has a higher priority than current exception priority, the processor wakes up but does not execute the interrupt handler until the processor clears PRIMASK. For more information about **PRIMASK** and **FAULTMASK**, see page 89 and page 90.

2.7.2.2 Wake Up from WFE

The processor wakes up if it detects an exception with sufficient priority to cause exception entry.

In addition, if the SEVONPEND bit in the **SYSCTRL** register is set, any new pending interrupt triggers an event and wakes up the processor, even if the interrupt is disabled or has insufficient priority to cause exception entry. For more information about **SYSCTRL**, see page 170.

2.8 Instruction Set Summary

The processor implements a version of the Thumb instruction set. Table 2-13 on page 119 lists the supported instructions.

Note: In Table 2-13 on page 119:

- Angle brackets, <>, enclose alternative forms of the operand
- Braces, {}, enclose optional operands
- The Operands column is not exhaustive
- Op2 is a flexible second operand that can be either a register or a constant
- Most instructions can use an optional condition code suffix

For more information on the instructions and operands, see the instruction descriptions in the *ARM*® *Cortex*™-*M4 Technical Reference Manual*.

Table 2-13. Cortex-M4F Instruction Summary

Mnemonic	Operands	Brief Description	Flags
ADC, ADCS	{Rd,} Rn, Op2	Add with carry	N,Z,C,V
ADD, ADDS	{Rd,} Rn, Op2	Add	N,Z,C,V
ADD, ADDW	{Rd,} Rn , #imm12	Add	-
ADR	Rd, label	Load PC-relative address	-
AND, ANDS	{Rd,} Rn, Op2	Logical AND	N,Z,C
ASR, ASRS	Rd, Rm, <rs #n></rs #n>	Arithmetic shift right	N,Z,C
В	label	Branch	-
BFC	Rd, #lsb, #width	Bit field clear	-
BFI	Rd, Rn, #lsb, #width	Bit field insert	-
BIC, BICS	{Rd,} Rn, Op2	Bit clear	N,Z,C
ВКРТ	#imm	Breakpoint	-
BL	label	Branch with link	-
BLX	Rm	Branch indirect with link	-
BX	Rm	Branch indirect	-
CBNZ	Rn, label	Compare and branch if non-zero	-

Table 2-13. Cortex-M4F Instruction Summary (continued)

Mnemonic	Operands	Brief Description	Flags
CBZ	Rn, label	Compare and branch if zero	-
CLREX	-	Clear exclusive	-
CLZ	Rd, Rm	Count leading zeros	-
CMN	Rn, Op2	Compare negative	N,Z,C,V
CMP	Rn, Op2	Compare	N,Z,C,V
CPSID	i	Change processor state, disable interrupts	-
CPSIE	i	Change processor state, enable interrupts	-
DMB	-	Data memory barrier	-
DSB	-	Data synchronization barrier	-
EOR, EORS	{Rd,} Rn, Op2	Exclusive OR	N,Z,C
ISB	-	Instruction synchronization barrier	-
IT	-	If-Then condition block	-
LDM	Rn{!}, reglist	Load multiple registers, increment after	-
LDMDB, LDMEA	Rn{!}, reglist	Load multiple registers, decrement before	-
LDMFD, LDMIA	Rn{!}, reglist	Load multiple registers, increment after	-
LDR	Rt, [Rn, #offset]	Load register with word	-
LDRB, LDRBT	Rt, [Rn, #offset]	Load register with byte	-
LDRD	Rt, Rt2, [Rn, #offset]	Load register with two bytes	-
LDREX	Rt, [Rn, #offset]	Load register exclusive	-
LDREXB	Rt, [Rn]	Load register exclusive with byte	-
LDREXH	Rt, [Rn]	Load register exclusive with halfword	-
LDRH, LDRHT	Rt, [Rn, #offset]	Load register with halfword	-
LDRSB, LDRSBT	Rt, [Rn, #offset]	Load register with signed byte	-
LDRSH, LDRSHT	Rt, [Rn, #offset]	Load register with signed halfword	-
LDRT	Rt, [Rn, #offset]	Load register with word	-
LSL, LSLS	Rd, Rm, <rs #n></rs #n>	Logical shift left	N,Z,C
LSR, LSRS	Rd, Rm, <rs #n></rs #n>	Logical shift right	N,Z,C
MLA	Rd, Rn, Rm, Ra	Multiply with accumulate, 32-bit result	-
MLS	Rd, Rn, Rm, Ra	Multiply and subtract, 32-bit result	-
MOV, MOVS	Rd, Op2	Move	N,Z,C
MOV, MOVW	Rd, #imm16	Move 16-bit constant	N,Z,C
MOVT	Rd, #imm16	Move top	-
MRS	Rd, spec_reg	Move from special register to general register	-
MSR	spec_reg, Rm	Move from general register to special register	N,Z,C,V
MUL, MULS	{Rd,} Rn, Rm	Multiply, 32-bit result	N,Z
MVN, MVNS	Rd, Op2	Move NOT	N,Z,C
NOP	-	No operation	-
ORN, ORNS	{Rd,} Rn, Op2	Logical OR NOT	N,Z,C

Table 2-13. Cortex-M4F Instruction Summary (continued)

Mnemonic	Operands	Brief Description	Flags
ORR, ORRS	{Rd,} Rn, Op2	Logical OR	N,Z,C
РКНТВ, РКНВТ	{Rd,} Rn, Rm, Op2	Pack halfword	-
POP	reglist	Pop registers from stack	-
PUSH	reglist	Push registers onto stack	-
QADD	{Rd,} Rn, Rm	Saturating add	Q
QADD16	{Rd,} Rn, Rm	Saturating add 16	-
QADD8	{Rd,} Rn, Rm	Saturating add 8	-
QASX	{Rd,} Rn, Rm	Saturating add and subtract with exchange	-
QDADD	{Rd,} Rn, Rm	Saturating double and add	Q
QDSUB	{Rd,} Rn, Rm	Saturating double and subtract	Q
QSAX	{Rd,} Rn, Rm	Saturating subtract and add with exchange	-
QSUB	{Rd,} Rn, Rm	Saturating subtract	Q
QSUB16	{Rd,} Rn, Rm	Saturating subtract 16	-
QSUB8	{Rd,} Rn, Rm	Saturating subtract 8	-
RBIT	Rd, Rn	Reverse bits	-
REV	Rd, Rn	Reverse byte order in a word	-
REV16	Rd, Rn	Reverse byte order in each halfword	-
REVSH	Rd, Rn	Reverse byte order in bottom halfword and sign extend	-
ROR, RORS	Rd, Rm, <rs #n></rs #n>	Rotate right	N,Z,C
RRX, RRXS	Rd, Rm	Rotate right with extend	N,Z,C
RSB, RSBS	{Rd,} Rn, Op2	Reverse subtract	N,Z,C,V
SADD16	{Rd,} Rn, Rm	Signed add 16	GE
SADD8	{Rd,} Rn, Rm	Signed add 8	GE
SASX	{Rd,} Rn, Rm	Signed add and subtract with exchange	GE
SBC, SBCS	{Rd,} Rn, Op2	Subtract with carry	N,Z,C,V
SBFX	Rd, Rn, #lsb, #width	Signed bit field extract	-
SDIV	{Rd,} Rn, Rm	Signed divide	-
SEL	{Rd,} Rn, Rm	Select bytes	-
SEV	-	Send event	-
SHADD16	{Rd,} Rn, Rm	Signed halving add 16	-
SHADD8	{Rd,} Rn, Rm	Signed halving add 8	-
SHASX	{Rd,} Rn, Rm	Signed halving add and subtract with exchange	-
SHSAX	{Rd,} Rn, Rm	Signed halving add and subtract with exchange	-
SHSUB16	{Rd,} Rn, Rm	Signed halving subtract 16	-
SHSUB8	{Rd,} Rn, Rm	Signed halving subtract 8	-
		1	1

Table 2-13. Cortex-M4F Instruction Summary (continued)

Mnemonic	Operands	Brief Description	Flags
SMLABB,	Rd, Rn, Rm, Ra	Signed multiply accumulate long	Q
SMLABT,		(halfwords)	
SMLATB,			
SMLATT			
SMLAD,	Rd, Rn, Rm, Ra	Signed multiply accumulate dual	Q
SMLADX			
SMLAL	RdLo, RdHi, Rn, Rm	Signed multiply with accumulate (32x32+64), 64-bit result	-
SMLALBB,	RdLo, RdHi, Rn, Rm	Signed multiply accumulate long	-
SMLALBT,		(halfwords)	
SMLALTB,			
SMLALTT			
SMLALD, SMLALDX	RdLo, RdHi, Rn, Rm	Signed multiply accumulate long dual	-
SMLAWB, SMLAWT	Rd, Rn, Rm, Ra	Signed multiply accumulate, word by halfword	Q
SMLSD	Rd, Rn, Rm, Ra	Signed multiply subtract dual	Q
SMLSDX			
SMLSLD	RdLo, RdHi, Rn, Rm	Signed multiply subtract long dual	
SMLSLDX			
SMMLA	Rd, Rn, Rm, Ra	Signed most significant word multiply accumulate	-
SMMLS,	Rd, Rn, Rm, Ra	Signed most significant word multiply	-
SMMLR		subtract	
SMMUL,	{Rd,} Rn, Rm	Signed most significant word multiply	-
SMMULR			
SMUAD	{Rd,} Rn, Rm	Signed dual multiply add	Q
SMUADX			
SMULBB,	{Rd,} Rn, Rm	Signed multiply halfwords	-
SMULBT,			
SMULTB,			
SMULTT			
SMULL	RdLo, RdHi, Rn, Rm	Signed multiply (32x32), 64-bit result	-
SMULWB,	{Rd,} Rn, Rm	Signed multiply by halfword	-
SMULWT			
SMUSD,	{Rd,} Rn, Rm	Signed dual multiply subtract	-
SMUSDX			
SSAT	Rd, #n, Rm {,shift #s}	Signed saturate	Q
SSAT16	Rd, #n, Rm	Signed saturate 16	Q
SSAX	{Rd,} Rn, Rm	Saturating subtract and add with exchange	GE
SSUB16	{Rd,} Rn, Rm	Signed subtract 16	-
SSUB8	{Rd,} Rn, Rm	Signed subtract 8	-
STM	Rn{!}, reglist	Store multiple registers, increment after	· _
O 11.1	Tur(.), regrisc	Otoro manipio registers, increment alter	1

Table 2-13. Cortex-M4F Instruction Summary (continued)

Mnemonic	Operands	Brief Description	Flags
STMDB, STMEA	Rn{!}, reglist	Store multiple registers, decrement before	-
STMFD, STMIA	Rn{!}, reglist	Store multiple registers, increment after	-
STR	Rt, [Rn {, #offset}]	Store register word	-
STRB, STRBT	Rt, [Rn {, #offset}]	Store register byte	-
STRD	Rt, Rt2, [Rn {, #offset}]	Store register two words	-
STREX	Rt, Rt, [Rn {, #offset}]	Store register exclusive	-
STREXB	Rd, Rt, [Rn]	Store register exclusive byte	-
STREXH	Rd, Rt, [Rn]	Store register exclusive halfword	-
STRH, STRHT	Rt, [Rn {, #offset}]	Store register halfword	-
STRSB, STRSBT	Rt, [Rn {, #offset}]	Store register signed byte	-
STRSH, STRSHT	Rt, [Rn {, #offset}]	Store register signed halfword	-
STRT	Rt, [Rn {, #offset}]	Store register word	-
SUB, SUBS	{Rd,} Rn, Op2	Subtract	N,Z,C,V
SUB, SUBW	{Rd,} Rn, #imm12	Subtract 12-bit constant	N,Z,C,V
SVC	#imm	Supervisor call	-
SXTAB	{Rd,} Rn, Rm, {,ROR #}	Extend 8 bits to 32 and add	-
SXTAB16	{Rd,} Rn, Rm,{,ROR #}	Dual extend 8 bits to 16 and add	-
SXTAH	{Rd,} Rn, Rm,{,ROR #}	Extend 16 bits to 32 and add	-
SXTB16	{Rd,} Rm {,ROR #n}	Signed extend byte 16	-
SXTB	{Rd,} Rm {,ROR #n}	Sign extend a byte	-
SXTH	{Rd,} Rm {,ROR #n}	Sign extend a halfword	-
TBB	[Rn, Rm]	Table branch byte	-
ГВН	[Rn, Rm, LSL #1]	Table branch halfword	-
TEQ	Rn, Op2	Test equivalence	N,Z,C
TST	Rn, Op2	Test	N,Z,C
JADD16	{Rd,} Rn, Rm	Unsigned add 16	GE
JADD8	{Rd,} Rn, Rm	Unsigned add 8	GE
JASX	{Rd,} Rn, Rm	Unsigned add and subtract with exchange	GE
JHADD16	{Rd,} Rn, Rm	Unsigned halving add 16	-
JHADD8	{Rd,} Rn, Rm	Unsigned halving add 8	-
JHASX	{Rd,} Rn, Rm	Unsigned halving add and subtract with exchange	-
JHSAX	{Rd,} Rn, Rm	Unsigned halving subtract and add with exchange	-
JHSUB16	{Rd,} Rn, Rm	Unsigned halving subtract 16	-
JHSUB8	{Rd,} Rn, Rm	Unsigned halving subtract 8	-
JBFX	Rd, Rn, #lsb, #width	Unsigned bit field extract	-
JDIV	{Rd,} Rn, Rm	Unsigned divide	-
UMAAL	RdLo, RdHi, Rn, Rm	Unsigned multiply accumulate accumulate long (32x32+64), 64-bit result	-

Table 2-13. Cortex-M4F Instruction Summary (continued)

Mnemonic	Operands	Brief Description	Flags
UMLAL	RdLo, RdHi, Rn, Rm	Unsigned multiply with accumulate (32x32+32+32), 64-bit result	-
UMULL	RdLo, RdHi, Rn, Rm	Unsigned multiply (32x 2), 64-bit result	-
UQADD16	{Rd,} Rn, Rm	Unsigned Saturating Add 16	-
UQADD8	{Rd,} Rn, Rm	Unsigned Saturating Add 8	-
UQASX	{Rd,} Rn, Rm	Unsigned Saturating Add and Subtract with Exchange	-
UQSAX	{Rd,} Rn, Rm	Unsigned Saturating Subtract and Add with Exchange	-
UQSUB16	{Rd,} Rn, Rm	Unsigned Saturating Subtract 16	-
UQSUB8	{Rd,} Rn, Rm	Unsigned Saturating Subtract 8	-
USAD8	{Rd,} Rn, Rm	Unsigned Sum of Absolute Differences	-
USADA8	{Rd,} Rn, Rm, Ra	Unsigned Sum of Absolute Differences and Accumulate	-
USAT	Rd, #n, Rm {,shift #s}	Unsigned Saturate	Q
USAT16	Rd, #n, Rm	Unsigned Saturate 16	Q
USAX	{Rd,} Rn, Rm	Unsigned Subtract and add with Exchange	GE
USUB16	{Rd,} Rn, Rm	Unsigned Subtract 16	GE
USUB8	{Rd,} Rn, Rm	Unsigned Subtract 8	GE
UXTAB	{Rd,} Rn, Rm, {,ROR #}	Rotate, extend 8 bits to 32 and Add	-
UXTAB16	{Rd,} Rn, Rm, {,ROR #}	Rotate, dual extend 8 bits to 16 and Add	-
UXTAH	{Rd,} Rn, Rm, {,ROR #}	Rotate, unsigned extend and Add Halfword	-
UXTB	{Rd,} Rm, {,ROR #n}	Zero extend a Byte	-
UXTB16	{Rd,} Rm, {,ROR #n}	Unsigned Extend Byte 16	-
UXTH	{Rd,} Rm, {,ROR #n}	Zero extend a Halfword	-
VABS.F32	Sd, Sm	Floating-point Absolute	-
VADD.F32	{Sd,} Sn, Sm	Floating-point Add	-
VCMP.F32	Sd, <sm #0.0="" =""></sm>	Compare two floating-point registers, or one floating-point register and zero	FPSCR
VCMPE.F32	Sd, <sm #0.0="" =""></sm>	Compare two floating-point registers, or one floating-point register and zero with Invalid Operation check	
VCVT.S32.F32	Sd, Sm	Convert between floating-point and integer	-
VCVT.S16.F32	Sd, Sd, #fbits	Convert between floating-point and fixed point	-
VCVTR.S32.F32	Sd, Sm	Convert between floating-point and integer with rounding	-
VCVT <b h>.F32.F16</b h>	Sd, Sm	Converts half-precision value to single-precision	-
VCVTT <b t>.F32.F16</b t>	Sd, Sm	Converts single-precision register to half-precision	-
VDIV.F32	{Sd,} Sn, Sm	Floating-point Divide	-
VFMA.F32	{Sd,} Sn, Sm	Floating-point Fused Multiply Accumulate	-

Table 2-13. Cortex-M4F Instruction Summary (continued)

Mnemonic	Operands	Brief Description	Flags
VFNMA.F32	{Sd,} Sn, Sm	Floating-point Fused Negate Multiply Accumulate	-
VFMS.F32	{Sd,} Sn, Sm	Floating-point Fused Multiply Subtract	-
VFNMS.F32	{Sd,} Sn, Sm	Floating-point Fused Negate Multiply Subtract	-
VLDM.F<32 64>	Rn{!}, list	Load Multiple extension registers	-
VLDR.F<32 64>	<dd sd>, [Rn]</dd sd>	Load an extension register from memory	-
VLMA.F32	{Sd,} Sn, Sm	Floating-point Multiply Accumulate	-
VLMS.F32	{Sd,} Sn, Sm	Floating-point Multiply Subtract	-
VMOV.F32	Sd, #imm	Floating-point Move immediate	-
VMOV	Sd, Sm	Floating-point Move register	-
VMOV	Sn, Rt	Copy ARM core register to single precision	-
VMOV	Sm, Sm1, Rt, Rt2	Copy 2 ARM core registers to 2 single precision	-
VMOV	Dd[x], Rt	Copy ARM core register to scalar	-
VMOV	Rt, Dn[x]	Copy scalar to ARM core register	-
VMRS	Rt, FPSCR	Move FPSCR to ARM core register or APSR	N,Z,C,V
VMSR	FPSCR, Rt	Move to FPSCR from ARM Core register	FPSCR
VMUL.F32	{Sd,} Sn, Sm	Floating-point Multiply	-
VNEG.F32	Sd, Sm	Floating-point Negate	-
VNMLA.F32	{Sd,} Sn, Sm	Floating-point Multiply and Add	-
VNMLS.F32	{Sd,} Sn, Sm	Floating-point Multiply and Subtract	-
VNMUL	{Sd,} Sn, Sm	Floating-point Multiply	-
VPOP	list	Pop extension registers	-
VPUSH	list	Push extension registers	-
VSQRT.F32	Sd, Sm	Calculates floating-point Square Root	-
VSTM	Rn{!}, list	Floating-point register Store Multiple	-
VSTR.F3<32 64>	Sd, [Rn]	Stores an extension register to memory	-
VSUB.F<32 64>	{Sd,} Sn, Sm	Floating-point Subtract	-
WFE	-	Wait for event	-
WFI	-	Wait for interrupt	-

3 Cortex-M4 Peripherals

This chapter provides information on the Stellaris[®] implementation of the Cortex-M4 processor peripherals, including:

■ SysTick (see page 127)

Provides a simple, 24-bit clear-on-write, decrementing, wrap-on-zero counter with a flexible control mechanism.

- Nested Vectored Interrupt Controller (NVIC) (see page 128)
 - Facilitates low-latency exception and interrupt handling
 - Controls power management
 - Implements system control registers
- System Control Block (SCB) (see page 129)

Provides system implementation information and system control, including configuration, control, and reporting of system exceptions.

■ Memory Protection Unit (MPU) (see page 129)

Supports the standard ARMv7 Protected Memory System Architecture (PMSA) model. The MPU provides full support for protection regions, overlapping protection regions, access permissions, and exporting memory attributes to the system.

■ Floating-Point Unit (FPU) (see page 134)

Fully supports single-precision add, subtract, multiply, divide, multiply and accumulate, and square root operations. It also provides conversions between fixed-point and floating-point data formats, and floating-point constant instructions.

Table 3-1 on page 126 shows the address map of the Private Peripheral Bus (PPB). Some peripheral register regions are split into two address regions, as indicated by two addresses listed.

Table 3-1	. Core Peripheral	Register Regions
-----------	-------------------	------------------

Address	Core Peripheral	Description (see page)
0xE000.E010-0xE000.E01F	System Timer	127
0xE000.E100-0xE000.E4EF	Nested Vectored Interrupt Controller	128
0xE000.EF00-0xE000.EF03		
0xE000.E008-0xE000.E00F	System Control Block	129
0xE000.ED00-0xE000.ED3F		
0xE000.ED90-0xE000.EDB8	Memory Protection Unit	129
0xE000.EF30-0xE000.EF44	Floating Point Unit	134

3.1 Functional Description

This chapter provides information on the Stellaris implementation of the Cortex-M4 processor peripherals: SysTick, NVIC, SCB and MPU.

3.1.1 System Timer (SysTick)

Cortex-M4 includes an integrated system timer, SysTick, which provides a simple, 24-bit clear-on-write, decrementing, wrap-on-zero counter with a flexible control mechanism. The counter can be used in several different ways, for example as:

- An RTOS tick timer that fires at a programmable rate (for example, 100 Hz) and invokes a SysTick routine.
- A high-speed alarm timer using the system clock.
- A variable rate alarm or signal timer—the duration is range-dependent on the reference clock used and the dynamic range of the counter.
- A simple counter used to measure time to completion and time used.
- An internal clock source control based on missing/meeting durations. The COUNT bit in the STCTRL control and status register can be used to determine if an action completed within a set duration, as part of a dynamic clock management control loop.

The timer consists of three registers:

- SysTick Control and Status (STCTRL): A control and status counter to configure its clock, enable the counter, enable the SysTick interrupt, and determine counter status.
- SysTick Reload Value (STRELOAD): The reload value for the counter, used to provide the counter's wrap value.
- SysTick Current Value (STCURRENT): The current value of the counter.

When enabled, the timer counts down on each clock from the reload value to zero, reloads (wraps) to the value in the **STRELOAD** register on the next clock edge, then decrements on subsequent clocks. Clearing the **STRELOAD** register disables the counter on the next wrap. When the counter reaches zero, the COUNT status bit is set. The COUNT bit clears on reads.

Writing to the **STCURRENT** register clears the register and the COUNT status bit. The write does not trigger the SysTick exception logic. On a read, the current value is the value of the register at the time the register is accessed.

The SysTick counter runs on either the system clock or the precision internal oscillator (PIOSC) divided by 4. If this clock signal is stopped for low power mode, the SysTick counter stops. SysTick can be kept running during Deep-sleep mode by setting the CLK_SRC bit in the SysTick Control and Status Register (STCTRL) register. Ensure software uses aligned word accesses to access the SysTick registers.

The SysTick counter reload and current value are undefined at reset; the correct initialization sequence for the SysTick counter is:

- 1. Program the value in the STRELOAD register.
- 2. Clear the **STCURRENT** register by writing to it with any value.
- 3. Configure the STCTRL register for the required operation.

Note: When the processor is halted for debugging, the counter does not decrement.

3.1.2 Nested Vectored Interrupt Controller (NVIC)

This section describes the Nested Vectored Interrupt Controller (NVIC) and the registers it uses. The NVIC supports:

- 85 interrupts.
- A programmable priority level of 0-7 for each interrupt. A higher level corresponds to a lower priority, so level 0 is the highest interrupt priority.
- Low-latency exception and interrupt handling.
- Level and pulse detection of interrupt signals.
- Dynamic reprioritization of interrupts.
- Grouping of priority values into group priority and subpriority fields.
- Interrupt tail-chaining.
- An external Non-maskable interrupt (NMI).

The processor automatically stacks its state on exception entry and unstacks this state on exception exit, with no instruction overhead, providing low latency exception handling.

3.1.2.1 Level-Sensitive and Pulse Interrupts

The processor supports both level-sensitive and pulse interrupts. Pulse interrupts are also described as edge-triggered interrupts.

A level-sensitive interrupt is held asserted until the peripheral deasserts the interrupt signal. Typically this happens because the ISR accesses the peripheral, causing it to clear the interrupt request. A pulse interrupt is an interrupt signal sampled synchronously on the rising edge of the processor clock. To ensure the NVIC detects the interrupt, the peripheral must assert the interrupt signal for at least one clock cycle, during which the NVIC detects the pulse and latches the interrupt.

When the processor enters the ISR, it automatically removes the pending state from the interrupt (see "Hardware and Software Control of Interrupts" on page 128 for more information). For a level-sensitive interrupt, if the signal is not deasserted before the processor returns from the ISR, the interrupt becomes pending again, and the processor must execute its ISR again. As a result, the peripheral can hold the interrupt signal asserted until it no longer needs servicing.

3.1.2.2 Hardware and Software Control of Interrupts

The Cortex-M4 latches all interrupts. A peripheral interrupt becomes pending for one of the following reasons:

- The NVIC detects that the interrupt signal is High and the interrupt is not active.
- The NVIC detects a rising edge on the interrupt signal.
- Software writes to the corresponding interrupt set-pending register bit, or to the **Software Trigger Interrupt (SWTRIG)** register to make a Software-Generated Interrupt pending. See the INT bit in the **PEND0** register on page 150 or **SWTRIG** on page 160.

A pending interrupt remains pending until one of the following:

- The processor enters the ISR for the interrupt, changing the state of the interrupt from pending to active. Then:
 - For a level-sensitive interrupt, when the processor returns from the ISR, the NVIC samples
 the interrupt signal. If the signal is asserted, the state of the interrupt changes to pending,
 which might cause the processor to immediately re-enter the ISR. Otherwise, the state of the
 interrupt changes to inactive.
 - For a pulse interrupt, the NVIC continues to monitor the interrupt signal, and if this is pulsed
 the state of the interrupt changes to pending and active. In this case, when the processor
 returns from the ISR the state of the interrupt changes to pending, which might cause the
 processor to immediately re-enter the ISR.
 - If the interrupt signal is not pulsed while the processor is in the ISR, when the processor returns from the ISR the state of the interrupt changes to inactive.
- Software writes to the corresponding interrupt clear-pending register bit
 - For a level-sensitive interrupt, if the interrupt signal is still asserted, the state of the interrupt does not change. Otherwise, the state of the interrupt changes to inactive.
 - For a pulse interrupt, the state of the interrupt changes to inactive, if the state was pending
 or to active, if the state was active and pending.

3.1.3 System Control Block (SCB)

The System Control Block (SCB) provides system implementation information and system control, including configuration, control, and reporting of the system exceptions.

3.1.4 Memory Protection Unit (MPU)

This section describes the Memory protection unit (MPU). The MPU divides the memory map into a number of regions and defines the location, size, access permissions, and memory attributes of each region. The MPU supports independent attribute settings for each region, overlapping regions, and export of memory attributes to the system.

The memory attributes affect the behavior of memory accesses to the region. The Cortex-M4 MPU defines eight separate memory regions, 0-7, and a background region.

When memory regions overlap, a memory access is affected by the attributes of the region with the highest number. For example, the attributes for region 7 take precedence over the attributes of any region that overlaps region 7.

The background region has the same memory access attributes as the default memory map, but is accessible from privileged software only.

The Cortex-M4 MPU memory map is unified, meaning that instruction accesses and data accesses have the same region settings.

If a program accesses a memory location that is prohibited by the MPU, the processor generates a memory management fault, causing a fault exception and possibly causing termination of the process in an OS environment. In an OS environment, the kernel can update the MPU region setting dynamically based on the process to be executed. Typically, an embedded OS uses the MPU for memory protection.

Configuration of MPU regions is based on memory types (see "Memory Regions, Types and Attributes" on page 99 for more information).

Table 3-2 on page 130 shows the possible MPU region attributes. See the section called "MPU Configuration for a Stellaris Microcontroller" on page 134 for guidelines for programming a microcontroller implementation.

Table 3-2. Memory Attributes Summary

Memory Type	Description	
Strongly Ordered	All accesses to Strongly Ordered memory occur in program order.	
Device	Memory-mapped peripherals	
Normal	Normal memory	

To avoid unexpected behavior, disable the interrupts before updating the attributes of a region that the interrupt handlers might access.

Ensure software uses aligned accesses of the correct size to access MPU registers:

- Except for the **MPU Region Attribute and Size (MPUATTR)** register, all MPU registers must be accessed with aligned word accesses.
- The MPUATTR register can be accessed with byte or aligned halfword or word accesses.

The processor does not support unaligned accesses to MPU registers.

When setting up the MPU, and if the MPU has previously been programmed, disable unused regions to prevent any previous region settings from affecting the new MPU setup.

3.1.4.1 Updating an MPU Region

To update the attributes for an MPU region, the MPU Region Number (MPUNUMBER), MPU Region Base Address (MPUBASE) and MPUATTR registers must be updated. Each register can be programmed separately or with a multiple-word write to program all of these registers. You can use the MPUBASEx and MPUATTRx aliases to program up to four regions simultaneously using an STM instruction.

Updating an MPU Region Using Separate Words

This example simple code configures one region:

Disable a region before writing new region settings to the MPU if you have previously enabled the region being changed. For example:

```
; R1 = region number
; R2 = size/enable
; R3 = attributes
; R4 = address
LDR R0,=MPUNUMBER ; 0xE000ED98, MPU region number register
```

```
STR R1, [R0, #0x0] ; Region Number
BIC R2, R2, #1 ; Disable
STRH R2, [R0, #0x8] ; Region Size and Enable
STR R4, [R0, #0x4] ; Region Base Address
STRH R3, [R0, #0xA] ; Region Attribute
ORR R2, #1 ; Enable
STRH R2, [R0, #0x8] ; Region Size and Enable
```

Software must use memory barrier instructions:

- Before MPU setup, if there might be outstanding memory transfers, such as buffered writes, that might be affected by the change in MPU settings.
- After MPU setup, if it includes memory transfers that must use the new MPU settings.

However, memory barrier instructions are not required if the MPU setup process starts by entering an exception handler, or is followed by an exception return, because the exception entry and exception return mechanism cause memory barrier behavior.

Software does not need any memory barrier instructions during MPU setup, because it accesses the MPU through the Private Peripheral Bus (PPB), which is a Strongly Ordered memory region.

For example, if all of the memory access behavior is intended to take effect immediately after the programming sequence, then a DSB instruction and an ISB instruction should be used. A DSB is required after changing MPU settings, such as at the end of context switch. An ISB is required if the code that programs the MPU region or regions is entered using a branch or call. If the programming sequence is entered using a return from exception, or by taking an exception, then an ISB is not required.

Updating an MPU Region Using Multi-Word Writes

The MPU can be programmed directly using multi-word writes, depending how the information is divided. Consider the following reprogramming:

```
; R1 = region number
; R2 = address
; R3 = size, attributes in one
LDR R0, =MPUNUMBER ; 0xE000ED98, MPU region number register
STR R1, [R0, #0x0] ; Region Number
STR R2, [R0, #0x4] ; Region Base Address
STR R3, [R0, #0x8] ; Region Attribute, Size and Enable
```

An STM instruction can be used to optimize this:

```
; R1 = region number
; R2 = address
; R3 = size, attributes in one
LDR R0, =MPUNUMBER ; 0xE000ED98, MPU region number register
STM R0, {R1-R3} ; Region number, address, attribute, size and enable
```

This operation can be done in two words for pre-packed information, meaning that the **MPU Region Base Address (MPUBASE)** register (see page 194) contains the required region number and has the VALID bit set. This method can be used when the data is statically packed, for example in a boot loader:

Subregions


Regions of 256 bytes or more are divided into eight equal-sized subregions. Set the corresponding bit in the SRD field of the **MPU Region Attribute and Size (MPUATTR)** register (see page 196) to disable a subregion. The least-significant bit of the SRD field controls the first subregion, and the most-significant bit controls the last subregion. Disabling a subregion means another region overlapping the disabled range matches instead. If no other enabled region overlaps the disabled subregion, the MPU issues a fault.

Regions of 32, 64, and 128 bytes do not support subregions. With regions of these sizes, the SRD field must be configured to 0×00 , otherwise the MPU behavior is unpredictable.

Example of SRD Use

Two regions with the same base address overlap. Region one is 128 KB, and region two is 512 KB. To ensure the attributes from region one apply to the first 128 KB region, configure the SRD field for region two to 0x03 to disable the first two subregions, as Figure 3-1 on page 132 shows.

Figure 3-1. SRD Use Example



3.1.4.2 MPU Access Permission Attributes

The access permission bits, TEX, S, C, B, AP, and XN of the **MPUATTR** register, control access to the corresponding memory region. If an access is made to an area of memory without the required permissions, then the MPU generates a permission fault.

Table 3-3 on page 132 shows the encodings for the TEX, C, B, and S access permission bits. All encodings are shown for completeness, however the current implementation of the Cortex-M4 does not support the concept of cacheability or shareability. Refer to the section called "MPU Configuration for a Stellaris Microcontroller" on page 134 for information on programming the MPU for Stellaris implementations.

Table 3-3. TEX, S, C, and B Bit Field Encoding

TEX	S	С	В	Memory Type	Shareability	Other Attributes
000b	x ^a	0	0	Strongly Ordered	Shareable	-
000	x ^a	0	1	Device	Shareable	-

Table 3-3. TEX, S, C, and B Bit Field Encoding (continued)

TEX	S	С	В	Memory Type	Shareability	Other Attributes
000	0	1	0	Normal	Not shareable	
000	1	1	0	Normal	Shareable	Outer and inner write-through. No write
000	0	1	1	Normal	Normal Not shareable	
000	1	1	1	Normal	Shareable	
001	0	0	0	Normal	Not shareable	Outer and inner
001	1	0	0	Normal	Shareable	noncacheable.
001	x ^a	0	1	Reserved encoding	-	-
001	x ^a	1	0	Reserved encoding	-	-
001	0	1	1	Normal	Not shareable	Outer and inner
001	1	1	1	Normal	Shareable	write-back. Write and read allocate.
010	x ^a	0	0	Device	Not shareable	Nonshared Device.
010	x ^a	0	1	Reserved encoding	-	-
010	x ^a	1	x ^a	Reserved encoding	-	-
1BB	0	Α	Α	Normal	Not shareable	Cached memory (BB =
1BB	1	Α	А	Normal	Shareable	outer policy, AA = inner policy).
						See Table 3-4 for the encoding of the AA and BB bits.

a. The MPU ignores the value of this bit.

Table 3-4 on page 133 shows the cache policy for memory attribute encodings with a $\pm \pm \times$ value in the range of 0x4-0x7.

Table 3-4. Cache Policy for Memory Attribute Encoding

Encoding, AA or BB	Corresponding Cache Policy
00	Non-cacheable
01	Write back, write and read allocate
10	Write through, no write allocate
11	Write back, no write allocate

Table 3-5 on page 133 shows the AP encodings in the **MPUATTR** register that define the access permissions for privileged and unprivileged software.

Table 3-5. AP Bit Field Encoding

AP Bit Field		Unprivileged Permissions	Description
000	No access	No access	All accesses generate a permission fault.
001	R/W	No access	Access from privileged software only.
010	R/W	RO	Writes by unprivileged software generate a permission fault.
011	R/W	R/W	Full access.
100	Unpredictable	Unpredictable	Reserved.
101	RO	No access	Reads by privileged software only.

Table 3-5. AP Bit Field Encoding (continued)

AP Bit Field		Unprivileged Permissions	Description
110	RO	RO	Read-only, by privileged or unprivileged software.
111	RO	RO	Read-only, by privileged or unprivileged software.

MPU Configuration for a Stellaris Microcontroller

Stellaris microcontrollers have only a single processor and no caches. As a result, the MPU should be programmed as shown in Table 3-6 on page 134.

Table 3-6. Memory Region Attributes for Stellaris Microcontrollers

Memory Region	TEX	S	С	В	Memory Type and Attributes
Flash memory	000b	0	1	0	Normal memory, non-shareable, write-through
Internal SRAM	000b	1	1	0	Normal memory, shareable, write-through
External SRAM	000b	1	1	1	Normal memory, shareable, write-back, write-allocate
Peripherals	000b	1	0	1	Device memory, shareable

In current Stellaris microcontroller implementations, the shareability and cache policy attributes do not affect the system behavior. However, using these settings for the MPU regions can make the application code more portable. The values given are for typical situations.

3.1.4.3 MPU Mismatch

When an access violates the MPU permissions, the processor generates a memory management fault (see "Exceptions and Interrupts" on page 96 for more information). The **MFAULTSTAT** register indicates the cause of the fault. See page 181 for more information.

3.1.5 Floating-Point Unit (FPU)

This section describes the Floating-Point Unit (FPU) and the registers it uses. The FPU provides:

- 32-bit instructions for single-precision (C float) data-processing operations
- Combined multiply and accumulate instructions for increased precision (Fused MAC)
- Hardware support for conversion, addition, subtraction, multiplication with optional accumulate, division, and square-root
- Hardware support for denormals and all IEEE rounding modes
- 32 dedicated 32-bit single-precision registers, also addressable as 16 double-word registers
- Decoupled three stage pipeline


The Cortex-M4F FPU fully supports single-precision add, subtract, multiply, divide, multiply and accumulate, and square root operations. It also provides conversions between fixed-point and floating-point data formats, and floating-point constant instructions. The FPU provides floating-point computation functionality that is compliant with the ANSI/IEEE Std 754-2008, IEEE Standard for Binary Floating-Point Arithmetic, referred to as the IEEE 754 standard. The FPU's single-precision extension registers can also be accessed as 16 doubleword registers for load, store, and move operations.

3.1.5.1 FPU Views of the Register Bank

The FPU provides an extension register file containing 32 single-precision registers. These can be viewed as:

- Sixteen 64-bit doubleword registers, D0-D15
- Thirty-two 32-bit single-word registers, S0-S31
- A combination of registers from the above views

Figure 3-2. FPU Register Bank



The mapping between the registers is as follows:

- S<2n> maps to the least significant half of D<n>
- S<2n+1> maps to the most significant half of D<n>

For example, you can access the least significant half of the value in D6 by accessing S12, and the most significant half of the elements by accessing S13.

3.1.5.2 Modes of Operation

The FPU provides three modes of operation to accommodate a variety of applications.

Full-Compliance mode. In Full-Compliance mode, the FPU processes all operations according to the IEEE 754 standard in hardware.

Flush-to-Zero mode. Setting the FZ bit of the Floating-Point Status and Control (FPSC) register enables Flush-to-Zero mode. In this mode, the FPU treats all subnormal input operands of arithmetic CDP operations as zeros in the operation. Exceptions that result from a zero operand are signalled appropriately. VABS, VNEG, and VMOV are not considered arithmetic CDP operations and are not affected by Flush-to-Zero mode. A result that is tiny, as described in the IEEE 754 standard, where the destination precision is smaller in magnitude than the minimum normal value before rounding, is replaced with a zero. The IDC bit in FPSC indicates when an input flush occurs. The UFC bit in FPSC indicates when a result flush occurs.

Default NaN mode. Setting the DN bit in the **FPSC** register enables default NaN mode. In this mode, the result of any arithmetic data processing operation that involves an input NaN, or that generates a NaN result, returns the default NaN. Propagation of the fraction bits is maintained only by VABS,

VNEG, and VMOV operations. All other CDP operations ignore any information in the fraction bits of an input NaN.

3.1.5.3 Compliance with the IEEE 754 standard

When Default NaN (DN) and Flush-to-Zero (FZ) modes are disabled, FPv4 functionality is compliant with the IEEE 754 standard in hardware. No support code is required to achieve this compliance.

3.1.5.4 Complete Implementation of the IEEE 754 standard

The Cortex-M4F floating point instruction set does not support all operations defined in the IEEE 754-2008 standard. Unsupported operations include, but are not limited to the following:

- Remainder
- Round floating-point number to integer-valued floating-point number
- Binary-to-decimal conversions
- Decimal-to-binary conversions
- Direct comparison of single-precision and double-precision values

The Cortex-M4 FPU supports fused MAC operations as described in the IEEE standard. For complete implementation of the IEEE 754-2008 standard, floating-point functionality must be augmented with library functions.

3.1.5.5 IEEE 754 standard implementation choices

NaN handling

All single-precision values with the maximum exponent field value and a nonzero fraction field are valid NaNs. A most-significant fraction bit of zero indicates a Signaling NaN (SNaN). A one indicates a Quiet NaN (QNaN). Two NaN values are treated as different NaNs if they differ in any bit. The below table shows the default NaN values.

Sign	Fraction	Fraction
0	0xFF	bit [22] = 1, bits [21:0] are all zeros

Processing of input NaNs for ARM floating-point functionality and libraries is defined as follows:

- In full-compliance mode, NaNs are handled as described in the ARM Architecture Reference Manual. The hardware processes the NaNs directly for arithmetic CDP instructions. For data transfer operations, NaNs are transferred without raising the Invalid Operation exception. For the non-arithmetic CDP instructions, VABS, VNEG, and VMOV, NaNs are copied, with a change of sign if specified in the instructions, without causing the Invalid Operation exception.
- In default NaN mode, arithmetic CDP instructions involving NaN operands return the default NaN regardless of the fractions of any NaN operands. SNaNs in an arithmetic CDP operation set the IOC flag, FPSCR[0]. NaN handling by data transfer and non-arithmetic CDP instructions is the same as in full-compliance mode.

Table 3-7. QNaN and SNaN Handling

	Default NaN Mode	With QNaN Operand	With SNaN Operand	
Arithmetic CDP	Off	The QNaN or one of the QNaN operands, if there is more than one, is returned according to the rules given in the ARM Architecture Reference Manual.	IOC ^a set. The SNaN is quieted and the result NaN is determined by the rules given in the ARM Architecture Reference Manual.	
	On	Default NaN returns.	IOCa set. Default NaN returns.	
Non-arithmetic CDP	Off/On	NaN passes to destination with sign changed as appropriate.		
FCMP(Z)	-	Unordered compare.	IOC set. Unordered compare.	
FCMPE(Z)	-	IOC set. Unordered compare.	IOC set. Unordered compare.	
Load/store	Off/On	All NaNs transferred.		

a. IOC is the Invalid Operation exception flag, FPSCR[0].

Comparisons

Comparison results modify the flags in the FPSCR. You can use the MVRS APSR_nzcv instruction (formerly FMSTAT) to transfer the current flags from the FPSCR to the APSR. See the ARM Architecture Reference Manual for mapping of IEEE 754-2008 standard predicates to ARM conditions. The flags used are chosen so that subsequent conditional execution of ARM instructions can test the predicates defined in the IEEE standard.

Underflow

The Cortex-M4F FPU uses the before rounding form of tininess and the inexact result form of loss of accuracy as described in the IEEE 754-2008 standard to generate Underflow exceptions.

In flush-to-zero mode, results that are tiny before rounding, as described in the IEEE standard, are flushed to a zero, and the UFC flag, FPSCR[3], is set. See the ARM Architecture Reference Manual for information on flush-to-zero mode.

When the FPU is not in flush-to-zero mode, operations are performed on subnormal operands. If the operation does not produce a tiny result, it returns the computed result, and the UFC flag, FPSCR[3], is not set. The IXC flag, FPSCR[4], is set if the operation is inexact. If the operation produces a tiny result, the result is a subnormal or zero value, and the UFC flag, FPSCR[3], is set if the result was also inexact.

3.1.5.6 Exceptions

The FPU sets the cumulative exception status flag in the FPSCR register as required for each instruction, in accordance with the FPv4 architecture. The FPU does not support user-mode traps. The exception enable bits in the FPSCR read-as-zero, and writes are ignored. The processor also has six output pins, FPIXC, FPUFC, FPOFC, FPDZC, FPIDC, and FPIOC, that each reflect the status of one of the cumulative exception flags. For a description of these outputs, see the *ARM Cortex-M4 Integration and Implementation Manual* (ARM DII 0239, available from ARM).

The processor can reduce the exception latency by using lazy stacking. See Auxiliary Control Register, ACTLR on page 4-5. This means that the processor reserves space on the stack for the FP state, but does not save that state information to the stack. See the ARMv7-M Architecture Reference Manual (available from ARM) for more information.

3.1.5.7 Enabling the FPU

The FPU is disabled from reset. You must enable it before you can use any floating-point instructions. The processor must be in privileged mode to read from and write to the **Coprocessor Access**

Control (CPAC) register. The below example code sequence enables the FPU in both privileged and user modes.

```
; CPACR is located at address 0xE000ED88
LDR.W R0, =0xE000ED88
; Read CPACR
LDR R1, [R0]
; Set bits 20-23 to enable CP10 and CP11 coprocessors
ORR R1, R1, #(0xF << 20)
; Write back the modified value to the CPACR
STR R1, [R0]; wait for store to complete
DSB
;reset pipeline now the FPU is enabled
ISB</pre>
```

3.2 Register Map

Table 3-8 on page 138 lists the Cortex-M4 Peripheral SysTick, NVIC, MPU, FPU and SCB registers. The offset listed is a hexadecimal increment to the register's address, relative to the Core Peripherals base address of 0xE000.E000.

Note: Register spaces that are not used are reserved for future or internal use. Software should not modify any reserved memory address.

Table 3-8. Peripherals Register Map

Offset	Name	Туре	Reset	Description	See page			
System T	System Timer (SysTick) Registers							
0x010	STCTRL	R/W	0x0000.0004	SysTick Control and Status Register	142			
0x014	STRELOAD	R/W	-	SysTick Reload Value Register	144			
0x018	STCURRENT	R/WC	-	SysTick Current Value Register	145			
Nested V	ectored Interrupt Control	ler (NVIC)	Registers		-			
0x100	EN0	R/W	0x0000.0000	Interrupt 0-31 Set Enable	146			
0x104	EN1	R/W	0x0000.0000	Interrupt 32-63 Set Enable	146			
0x108	EN2	R/W	0x0000.0000	Interrupt 64-95 Set Enable	146			
0x10C	EN3	R/W	0x0000.0000	Interrupt 96-127 Set Enable	146			
0x110	EN4	R/W	0x0000.0000	Interrupt 128-138 Set Enable	147			
0x180	DIS0	R/W	0x0000.0000	Interrupt 0-31 Clear Enable	148			
0x184	DIS1	R/W	0x0000.0000	Interrupt 32-63 Clear Enable	148			
0x188	DIS2	R/W	0x0000.0000	Interrupt 64-95 Clear Enable	148			
0x18C	DIS3	R/W	0x0000.0000	Interrupt 96-127 Clear Enable	148			
0x190	DIS4	R/W	0x0000.0000	Interrupt 128-138 Clear Enable	149			
0x200	PEND0	R/W	0x0000.0000	Interrupt 0-31 Set Pending	150			
0x204	PEND1	R/W	0x0000.0000	Interrupt 32-63 Set Pending	150			

Table 3-8. Peripherals Register Map (continued)

Offset	et Name Type Reset		Description	See page	
0x208	PEND2	R/W	0x0000.0000	Interrupt 64-95 Set Pending	150
0x20C	PEND3	R/W	0x0000.0000	Interrupt 96-127 Set Pending	150
0x210	PEND4	R/W	0x0000.0000	Interrupt 128-138 Set Pending	151
0x280	UNPEND0	R/W	0x0000.0000	Interrupt 0-31 Clear Pending	152
0x284	UNPEND1	R/W	0x0000.0000	Interrupt 32-63 Clear Pending	152
0x288	UNPEND2	R/W	0x0000.0000	Interrupt 64-95 Clear Pending	152
0x28C	UNPEND3	R/W	0x0000.0000	Interrupt 96-127 Clear Pending	152
0x290	UNPEND4	R/W	0x0000.0000	Interrupt 128-138 Clear Pending	153
0x300	ACTIVE0	RO	0x0000.0000	Interrupt 0-31 Active Bit	154
0x304	ACTIVE1	RO	0x0000.0000	Interrupt 32-63 Active Bit	154
0x308	ACTIVE2	RO	0x0000.0000	Interrupt 64-95 Active Bit	154
0x30C	ACTIVE3	RO	0x0000.0000	Interrupt 96-127 Active Bit	154
0x310	ACTIVE4	RO	0x0000.0000	Interrupt 128-138 Active Bit	155
0x400	PRI0	R/W	0x0000.0000	Interrupt 0-3 Priority	156
0x404	PRI1	R/W	0x0000.0000	Interrupt 4-7 Priority	156
0x408	PRI2	R/W	0x0000.0000	Interrupt 8-11 Priority	156
0x40C	PRI3	R/W	0x0000.0000	Interrupt 12-15 Priority	156
0x410	PRI4	R/W	0x0000.0000	Interrupt 16-19 Priority	156
0x414	PRI5	R/W	0x0000.0000	Interrupt 20-23 Priority	156
0x418	PRI6	R/W	0x0000.0000	Interrupt 24-27 Priority	156
0x41C	PRI7	R/W	0x0000.0000	Interrupt 28-31 Priority	156
0x420	PRI8	R/W	0x0000.0000	Interrupt 32-35 Priority	156
0x424	PRI9	R/W	0x0000.0000	Interrupt 36-39 Priority	156
0x428	PRI10	R/W	0x0000.0000	Interrupt 40-43 Priority	156
0x42C	PRI11	R/W	0x0000.0000	Interrupt 44-47 Priority	156
0x430	PRI12	R/W	0x0000.0000	Interrupt 48-51 Priority	156
0x434	PRI13	R/W	0x0000.0000	Interrupt 52-55 Priority	156
0x438	PRI14	R/W	0x0000.0000	Interrupt 56-59 Priority	156
0x43C	PRI15	R/W	0x0000.0000	Interrupt 60-63 Priority	156
0x440	PRI16	R/W	0x0000.0000	Interrupt 64-67 Priority	158
0x444	PRI17	R/W	0x0000.0000	Interrupt 68-71 Priority	158
0x448	PRI18	R/W	0x0000.0000	Interrupt 72-75 Priority	158

Table 3-8. Peripherals Register Map (continued)

Offset	Name	me Type Reset		Description	See page
0x44C	PRI19	R/W	0x0000.0000	Interrupt 76-79 Priority	158
0x450	PRI20	R/W	0x0000.0000	Interrupt 80-83 Priority	158
0x454	PRI21	R/W	0x0000.0000	Interrupt 84-87 Priority	158
0x458	PRI22	R/W	0x0000.0000	Interrupt 88-91 Priority	158
0x45C	PRI23	R/W	0x0000.0000	Interrupt 92-95 Priority	158
0x460	PRI24	R/W	0x0000.0000	Interrupt 96-99 Priority	158
0x464	PRI25	R/W	0x0000.0000	Interrupt 100-103 Priority	158
0x468	PRI26	R/W	0x0000.0000	Interrupt 104-107 Priority	158
0x46C	PRI27	R/W	0x0000.0000	Interrupt 108-111 Priority	158
0x470	PRI28	R/W	0x0000.0000	Interrupt 112-115 Priority	158
0x474	PRI29	R/W	0x0000.0000	Interrupt 116-119 Priority	158
0x478	PRI30	R/W	0x0000.0000	Interrupt 120-123 Priority	158
0x47C	PRI31	R/W	0x0000.0000	Interrupt 124-127 Priority	158
0x480	PRI32	R/W	0x0000.0000	Interrupt 128-131 Priority	158
0x484	PRI33	R/W	0x0000.0000	Interrupt 132-135 Priority	158
0x488	PRI34	R/W	0x0000.0000	Interrupt 136-138 Priority	158
0xF00	SWTRIG	WO	0x0000.0000	Software Trigger Interrupt	160
System C	ontrol Block (SCB) Regi	sters			
0x008	ACTLR	R/W	0x0000.0000	Auxiliary Control	161
0xD00	CPUID	RO	0x410F.C241	CPU ID Base	163
0xD04	INTCTRL	R/W	0x0000.0000	Interrupt Control and State	164
0xD08	VTABLE	R/W	0x0000.0000	Vector Table Offset	167
0xD0C	APINT	R/W	0xFA05.0000	Application Interrupt and Reset Control	168
0xD10	SYSCTRL	R/W	0x0000.0000	System Control	170
0xD14	CFGCTRL	R/W	0x0000.0200	Configuration and Control	172
0xD18	SYSPRI1	R/W	0x0000.0000	System Handler Priority 1	174
0xD1C	SYSPRI2	R/W	0x0000.0000	System Handler Priority 2	175
0xD20	SYSPRI3	R/W	0x0000.0000	System Handler Priority 3	176
0xD24	SYSHNDCTRL	R/W	0x0000.0000	System Handler Control and State	177
0xD28	FAULTSTAT	R/W1C	0x0000.0000	Configurable Fault Status	181
0xD2C	HFAULTSTAT	R/W1C	0x0000.0000	Hard Fault Status	187
0xD34	MMADDR	R/W		Memory Management Fault Address	188

Table 3-8. Peripherals Register Map (continued)

Offset	Name	Туре	Reset	Description	See page
0xD38	FAULTADDR	R/W	-	Bus Fault Address	189
Memory F	Protection Unit (MPU) Re	gisters			'
0xD90	MPUTYPE	RO	0x0000.0800	MPU Type	190
0xD94	MPUCTRL	R/W	0x0000.0000	MPU Control	191
0xD98	MPUNUMBER	R/W	0x0000.0000	MPU Region Number	193
0xD9C	MPUBASE	R/W	0x0000.0000	MPU Region Base Address	194
0xDA0	MPUATTR	R/W	0x0000.0000	MPU Region Attribute and Size	196
0xDA4	MPUBASE1	R/W	0x0000.0000	MPU Region Base Address Alias 1	194
0xDA8	MPUATTR1	R/W	0x0000.0000	MPU Region Attribute and Size Alias 1	196
0xDAC	MPUBASE2	R/W	0x0000.0000	MPU Region Base Address Alias 2	194
0xDB0	MPUATTR2	R/W	0x0000.0000	MPU Region Attribute and Size Alias 2	196
0xDB4	MPUBASE3	R/W	0x0000.0000	MPU Region Base Address Alias 3	194
0xDB8	MPUATTR3	R/W	0x0000.0000	MPU Region Attribute and Size Alias 3	196
Floating-	Point Unit (FPU) Register	s			
0xD88	CPAC	R/W	0x0000.0000	Coprocessor Access Control	199
0xF34	FPCC	R/W	0xC000.0000	Floating-Point Context Control	200
0xF38	FPCA	R/W	-	Floating-Point Context Address	202
0xF3C	FPDSC	R/W	0x0000.0000	Floating-Point Default Status Control	203

3.3 System Timer (SysTick) Register Descriptions

This section lists and describes the System Timer registers, in numerical order by address offset.

Register 1: SysTick Control and Status Register (STCTRL), offset 0x010

Note: This register can only be accessed from privileged mode.

The SysTick **STCTRL** register enables the SysTick features.

SysTick Control and Status Register (STCTRL)

Base 0xE000.E000 Offset 0x010 Type R/W, reset 0x0000.0004

Type	17/11/10/10/10/10															
ı	31	30	29 1	28	27 I	26 I	25	24	23	22	21	20	19	18	17	16
					<u> </u>			reserved								COUNT
Type Reset	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0
	15	14	13	12	11	10	9	8	7	6	5	4	3	2	1	0
	10		1	1	· · ·	1	reserved	-	· ·	1	1			CLK_SRC	INTEN	ENABLE
Type	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	R/W	R/W	R/W
Reset	0	0	0	0	0	0	0	0	0	0	0	0	0	1	0	0
Bit/Field		l Name		Ту	Type Reset		Description									
	04:47				0000	0 - 4				la a la			T	2.4.		
31:17			reser	vea	R	.0	0x000	Software should not rely on the value of a reserved bit. To compatibility with future products, the value of a reserved preserved across a read-modify-write operation.								
16			COU	NT	R	0	0	Count Flag								
								Valı	ue	Descri	ption					
								0		-	sTick tim was rea		ot count	ed to 0 sir	nce the I	ast time
								1		-	/sTick tin was rea		ounted	to 0 since	e the las	t time
										eared by th any va		the regis	ter or if	the STCU	IRRENT	register
										•		the DAI	P, this b	it is cleare	ed only i	f the
								Mas	terTyp	e bit in t	he AHB	AP Con	trol Reg	gister is c	lear. Ot	herwise,
								Deb		face V5	•	•		er read. Se n for more		
	15:3		reser	ved	R	0	0x000	com	patibility	with fut	ure prod		value o	served bit f a reserv on.		
	2		CLK_S	SRC	R/	W	1	Clock Source								
								Valı	ue Desc	cription						
								0			ernal osc	illator (P	IOSC) c	divided by	4	

System clock

Bit/Field	Name	Туре	Reset	Description	on
1	INTEN	R/W	0	Interrupt Enable	
				Value	Description
				0	Interrupt generation is disabled. Software can use the COUNT bit to determine if the counter has ever reached 0.
				1	An interrupt is generated to the NVIC when SysTick counts to 0.
0	ENABLE	R/W	0	Enable	
				Value	Description
				0	The counter is disabled.
				1	Enables SysTick to operate in a multi-shot way. That is, the counter loads the RELOAD value and begins counting down. On reaching 0, the COUNT bit is set and an interrupt is generated if enabled by INTEN. The counter then loads the RELOAD value again and begins counting.

February 20, 2013 143

Register 2: SysTick Reload Value Register (STRELOAD), offset 0x014

Note: This register can only be accessed from privileged mode.


The **STRELOAD** register specifies the start value to load into the **SysTick Current Value** (**STCURRENT**) register when the counter reaches 0. The start value can be between 0x1 and 0x00FF.FFFF. A start value of 0 is possible but has no effect because the SysTick interrupt and the COUNT bit are activated when counting from 1 to 0.

SysTick can be configured as a multi-shot timer, repeated over and over, firing every N+1 clock pulses, where N is any value from 1 to 0x00FF.FFFF. For example, if a tick interrupt is required every 100 clock pulses, 99 must be written into the RELOAD field.

Note that in order to access this register correctly, the system clock must be faster than 8 MHz.

SysTick Reload Value Register (STRELOAD)

Base 0xE000.E000 Offset 0x014 Type R/W, reset -



Bit/Fie	d Name	Туре	Reset	Description
31:24	reserved	RO	0x00	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
23:0	RELOAD	R/W	0x00.0000	Reload Value

Value to load into the $\mbox{\bf SysTick}$ Current Value (STCURRENT) register when the counter reaches 0.


Register 3: SysTick Current Value Register (STCURRENT), offset 0x018

Note: This register can only be accessed from privileged mode.

The **STCURRENT** register contains the current value of the SysTick counter.

SysTick Current Value Register (STCURRENT)

Base 0xE000.E000 Offset 0x018 Type R/WC, reset -



No read-modify-write protection is provided, so change with care.

This register is write-clear. Writing to it with any value clears the register.

Clearing this register also clears the COUNT bit of the STCTRL register.

3.4 NVIC Register Descriptions

This section lists and describes the NVIC registers, in numerical order by address offset.

The NVIC registers can only be fully accessed from privileged mode, but interrupts can be pended while in unprivileged mode by enabling the **Configuration and Control (CFGCTRL)** register. Any other unprivileged mode access causes a bus fault.

Ensure software uses correctly aligned register accesses. The processor does not support unaligned accesses to NVIC registers.

An interrupt can enter the pending state even if it is disabled.

Before programming the **VTABLE** register to relocate the vector table, ensure the vector table entries of the new vector table are set up for fault handlers, NMI, and all enabled exceptions such as interrupts. For more information, see page 167.

Register 4: Interrupt 0-31 Set Enable (EN0), offset 0x100

Register 5: Interrupt 32-63 Set Enable (EN1), offset 0x104

Register 6: Interrupt 64-95 Set Enable (EN2), offset 0x108

Register 7: Interrupt 96-127 Set Enable (EN3), offset 0x10C

Note: This register can only be accessed from privileged mode.

The **ENn** registers enable interrupts and show which interrupts are enabled. Bit 0 of **EN0** corresponds to Interrupt 0; bit 31 corresponds to Interrupt 31. Bit 0 of **EN1** corresponds to Interrupt 32; bit 31 corresponds to Interrupt 63. Bit 0 of **EN2** corresponds to Interrupt 64; bit 31 corresponds to Interrupt 95. Bit 0 of **EN3** corresponds to Interrupt 96; bit 31 corresponds to Interrupt 127. Bit 0 of **EN4** (see page 147) corresponds to Interrupt 128; bit 10 corresponds to Interrupt 138.

See Table 2-9 on page 108 for interrupt assignments.

R/W

If a pending interrupt is enabled, the NVIC activates the interrupt based on its priority. If an interrupt is not enabled, asserting its interrupt signal changes the interrupt state to pending, but the NVIC never activates the interrupt, regardless of its priority.


Interrupt 0-31 Set Enable (EN0)

INT

Base 0xE000.E000 Offset 0x100

31.0

Type R/W, reset 0x0000.0000



0x0000.0000 Interrupt Enable

,	Value	Description
	0	On a read, indicates the interrupt is disabled.
		On a write, no effect.
	1	On a read, indicates the interrupt is enabled.

A bit can only be cleared by setting the corresponding ${\tt INT[n]}$ bit in the **DISn** register.

On a write, enables the interrupt.

Register 8: Interrupt 128-138 Set Enable (EN4), offset 0x110

Note: This register can only be accessed from privileged mode.


The **EN4** register enables interrupts and shows which interrupts are enabled. Bit 0 corresponds to Interrupt 128; bit 10 corresponds to Interrupt 138. See Table 2-9 on page 108 for interrupt assignments.

If a pending interrupt is enabled, the NVIC activates the interrupt based on its priority. If an interrupt is not enabled, asserting its interrupt signal changes the interrupt state to pending, but the NVIC never activates the interrupt, regardless of its priority.

Interrupt 128-138 Set Enable (EN4)

Base 0xE000.E000 Offset 0x110

Type R/W, reset 0x0000.0000



Bit/Field	Name	Type	Reset	Description
31:11	reserved	RO	0x0000.000	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
10:0	INT	R/W	0x0	Interrupt Enable

Value	Description
0	On a read, indicates the interrupt is disabled.
	On a write, no effect.
1	On a read, indicates the interrupt is enabled.
	On a write, enables the interrupt.

A bit can only be cleared by setting the corresponding ${\tt INT[n]}$ bit in the **DIS4** register.

Register 9: Interrupt 0-31 Clear Enable (DIS0), offset 0x180

Register 10: Interrupt 32-63 Clear Enable (DIS1), offset 0x184

Register 11: Interrupt 64-95 Clear Enable (DIS2), offset 0x188

Register 12: Interrupt 96-127 Clear Enable (DIS3), offset 0x18C

Note: This register can only be accessed from privileged mode.


The **DISn** registers disable interrupts. Bit 0 of **DIS0** corresponds to Interrupt 0; bit 31 corresponds to Interrupt 31. Bit 0 of **DIS1** corresponds to Interrupt 32; bit 31 corresponds to Interrupt 63. Bit 0 of **DIS2** corresponds to Interrupt 64; bit 31 corresponds to Interrupt 95. Bit 0 of **DIS3** corresponds to Interrupt 96; bit 31 corresponds to Interrupt 127. Bit 0 of **DIS4** (see page 149) corresponds to Interrupt 128; bit 10 corresponds to Interrupt 138.

See Table 2-9 on page 108 for interrupt assignments.

Interrupt 0-31 Clear Enable (DIS0)

Base 0xE000.E000 Offset 0x180

Type R/W, reset 0x0000.0000



Value Description

- On a read, indicates the interrupt is disabled.
 - On a write, no effect.
- 1 On a read, indicates the interrupt is enabled.

On a write, clears the corresponding INT[n] bit in the **EN0** register, disabling interrupt [n].

Register 13: Interrupt 128-138 Clear Enable (DIS4), offset 0x190


Note: This register can only be accessed from privileged mode.

The **DIS4** register disables interrupts. Bit 0 corresponds to Interrupt 128; bit 10 corresponds to Interrupt 138. See Table 2-9 on page 108 for interrupt assignments.

Interrupt 128-138 Clear Enable (DIS4)

Base 0xE000.E000

Offset 0x190 Type R/W, reset 0x0000.0000



Bit/Field	Name	Type	Reset	Description
31:11	reserved	RO	0x0000.000	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
10:0	INT	R/W	0x0	Interrupt Disable

- On a read, indicates the interrupt is disabled. On a write, no effect.
- On a read, indicates the interrupt is enabled. On a write, clears the corresponding INT[n] bit in the EN4 register, disabling interrupt [n].

Register 14: Interrupt 0-31 Set Pending (PEND0), offset 0x200

Register 15: Interrupt 32-63 Set Pending (PEND1), offset 0x204

Register 16: Interrupt 64-95 Set Pending (PEND2), offset 0x208

Register 17: Interrupt 96-127 Set Pending (PEND3), offset 0x20C

Note: This register can only be accessed from privileged mode.


The **PENDn** registers force interrupts into the pending state and show which interrupts are pending. Bit 0 of **PEND0** corresponds to Interrupt 0; bit 31 corresponds to Interrupt 31. Bit 0 of **PEND1** corresponds to Interrupt 32; bit 31 corresponds to Interrupt 63. Bit 0 of **PEND2** corresponds to Interrupt 64; bit 31 corresponds to Interrupt 95. Bit 0 of **PEND3** corresponds to Interrupt 96; bit 31 corresponds to Interrupt 127. Bit 0 of **PEND4** (see page 151) corresponds to Interrupt 128; bit 10 corresponds to Interrupt 138.

See Table 2-9 on page 108 for interrupt assignments.

Interrupt 0-31 Set Pending (PEND0)

Base 0xE000.E000 Offset 0x200

Type R/W, reset 0x0000.0000



Divi ielu	Name	Туре	Neset	Description
31:0	INT	R/W	0x0000.0000	Interrupt Set Pending

Value	Description
0	On a read, indicates that the interrupt is not pending.
	On a write, no effect.
1	On a read, indicates that the interrupt is pending.
	On a write, the corresponding interrupt is set to pending
	even if it is disabled

If the corresponding interrupt is already pending, setting a bit has no effect.

A bit can only be cleared by setting the corresponding ${\tt INT[n]}$ bit in the ${\bf UNPEND0}$ register.

Register 18: Interrupt 128-138 Set Pending (PEND4), offset 0x210

Note: This register can only be accessed from privileged mode.


The **PEND4** register forces interrupts into the pending state and shows which interrupts are pending. Bit 0 corresponds to Interrupt 128; bit 10 corresponds to Interrupt 138. See Table 2-9 on page 108 for interrupt assignments.

Interrupt 128-138 Set Pending (PEND4)

Base 0xE000.E000 Offset 0x210

D:4/E:-14

Type R/W, reset 0x0000.0000



Bit/Field	Name	туре	Reset	Description
31:11	reserved	RO	0x0000.000	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
10:0	INT	R/W	0x0	Interrupt Set Pending

Value	Description
0	On a read, indicates that the interrupt is not pending.
	On a write, no effect.
1	On a read, indicates that the interrupt is pending.
	On a write, the corresponding interrupt is set to pending even if it is disabled.

If the corresponding interrupt is already pending, setting a bit has no effect.

A bit can only be cleared by setting the corresponding ${\tt INT[n]}$ bit in the <code>UNPEND4</code> register.

Register 19: Interrupt 0-31 Clear Pending (UNPEND0), offset 0x280

Register 20: Interrupt 32-63 Clear Pending (UNPEND1), offset 0x284

Register 21: Interrupt 64-95 Clear Pending (UNPEND2), offset 0x288

Register 22: Interrupt 96-127 Clear Pending (UNPEND3), offset 0x28C

Note: This register can only be accessed from privileged mode.


The **UNPENDn** registers show which interrupts are pending and remove the pending state from interrupts. Bit 0 of **UNPEND0** corresponds to Interrupt 0; bit 31 corresponds to Interrupt 31. Bit 0 of **UNPEND1** corresponds to Interrupt 32; bit 31 corresponds to Interrupt 63. Bit 0 of **UNPEND2** corresponds to Interrupt 64; bit 31 corresponds to Interrupt 95. Bit 0 of **UNPEND3** corresponds to Interrupt 96; bit 31 corresponds to Interrupt 127. Bit 0 of **UNPEND4** (see page 153) corresponds to Interrupt 128; bit 10 corresponds to Interrupt 138.

See Table 2-9 on page 108 for interrupt assignments.

Interrupt 0-31 Clear Pending (UNPEND0)

Base 0xE000.E000 Offset 0x280

Type R/W, reset 0x0000.0000



1

- On a read, indicates that the interrupt is not pending.
 On a write, no effect.
 - On a read, indicates that the interrupt is pending.
 - On a write, clears the corresponding INT[n] bit in the **PEND0** register, so that interrupt [n] is no longer pending.
 - Setting a bit does not affect the active state of the corresponding interrupt.

Register 23: Interrupt 128-138 Clear Pending (UNPEND4), offset 0x290

Note: This register can only be accessed from privileged mode.


The **UNPEND4** register shows which interrupts are pending and removes the pending state from interrupts. Bit 0 corresponds to Interrupt 128; bit 10 corresponds to Interrupt 138. See Table 2-9 on page 108 for interrupt assignments.

Interrupt 128-138 Clear Pending (UNPEND4)

Base 0xE000.E000 Offset 0x290

D:4/E:-14

Type R/W, reset 0x0000.0000



Bivrieid	ivame	туре	Reset	Description
31:11	reserved	RO	0x0000.000	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
10:0	INT	R/W	0x0	Interrupt Clear Pending

- On a read, indicates that the interrupt is not pending. On a write, no effect.
- On a read, indicates that the interrupt is pending.

 On a write, clears the corresponding INT[n] bit in the **PEND4** register, so that interrupt [n] is no longer pending.

 Setting a bit does not affect the active state of the corresponding interrupt.

Register 24: Interrupt 0-31 Active Bit (ACTIVE0), offset 0x300

Register 25: Interrupt 32-63 Active Bit (ACTIVE1), offset 0x304

Register 26: Interrupt 64-95 Active Bit (ACTIVE2), offset 0x308

Register 27: Interrupt 96-127 Active Bit (ACTIVE3), offset 0x30C

Note: This register can only be accessed from privileged mode.

The **UNPENDn** registers indicate which interrupts are active. Bit 0 of **ACTIVE0** corresponds to Interrupt 0; bit 31 corresponds to Interrupt 31. Bit 0 of **ACTIVE1** corresponds to Interrupt 32; bit 31 corresponds to Interrupt 63. Bit 0 of **ACTIVE2** corresponds to Interrupt 64; bit 31 corresponds to Interrupt 95. Bit 0 of **ACTIVE3** corresponds to Interrupt 96; bit 31 corresponds to Interrupt 127. Bit 0 of **ACTIVE4** (see page 155) corresponds to Interrupt 128; bit 10 corresponds to Interrupt 138.


See Table 2-9 on page 108 for interrupt assignments.

Caution – Do not manually set or clear the bits in this register.

Interrupt 0-31 Active Bit (ACTIVE0)

Base 0xE000.E000 Offset 0x300

Type RO, reset 0x0000.0000



Bit/Field Name Type Reset Description

31:0 INT RO 0x0000.0000 Interrupt Active

- 0 The corresponding interrupt is not active.
- 1 The corresponding interrupt is active, or active and pending.

Register 28: Interrupt 128-138 Active Bit (ACTIVE4), offset 0x310


Note: This register can only be accessed from privileged mode.

The ACTIVE4 register indicates which interrupts are active. Bit 0 corresponds to Interrupt 128; bit 10 corresponds to Interrupt 131. See Table 2-9 on page 108 for interrupt assignments.

Caution – Do not manually set or clear the bits in this register.

Interrupt 128-138 Active Bit (ACTIVE4)

Base 0xE000.E000 Offset 0x310 Type RO, reset 0x0000.0000



Bit/Field	Name	Type	Reset	Description
31:11	reserved	RO	0x0000.000	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
10:0	INT	RO	0x0	Interrupt Active

- 0 The corresponding interrupt is not active.
- 1 The corresponding interrupt is active, or active and pending.

Register 29: Interrupt 0-3 Priority (PRI0), offset 0x400 Register 30: Interrupt 4-7 Priority (PRI1), offset 0x404 Register 31: Interrupt 8-11 Priority (PRI2), offset 0x408 Register 32: Interrupt 12-15 Priority (PRI3), offset 0x40C Register 33: Interrupt 16-19 Priority (PRI4), offset 0x410 Register 34: Interrupt 20-23 Priority (PRI5), offset 0x414 Register 35: Interrupt 24-27 Priority (PRI6), offset 0x418 Register 36: Interrupt 28-31 Priority (PRI7), offset 0x41C Register 37: Interrupt 32-35 Priority (PRI8), offset 0x420 Register 38: Interrupt 36-39 Priority (PRI9), offset 0x424 Register 39: Interrupt 40-43 Priority (PRI10), offset 0x428 Register 40: Interrupt 44-47 Priority (PRI11), offset 0x42C Register 41: Interrupt 48-51 Priority (PRI12), offset 0x430 Register 42: Interrupt 52-55 Priority (PRI13), offset 0x434 Register 43: Interrupt 56-59 Priority (PRI14), offset 0x438 Register 44: Interrupt 60-63 Priority (PRI15), offset 0x43C

Note: This register can only be accessed from privileged mode.

The **PRIn** registers (see also page 158) provide 3-bit priority fields for each interrupt. These registers are byte accessible. Each register holds four priority fields that are assigned to interrupts as follows:

PRIn Register Bit Field	Interrupt
Bits 31:29	Interrupt [4n+3]
Bits 23:21	Interrupt [4n+2]
Bits 15:13	Interrupt [4n+1]
Bits 7:5	Interrupt [4n]

See Table 2-9 on page 108 for interrupt assignments.

Each priority level can be split into separate group priority and subpriority fields. The PRIGROUP field in the **Application Interrupt and Reset Control (APINT)** register (see page 168) indicates the position of the binary point that splits the priority and subpriority fields.

These registers can only be accessed from privileged mode.

Interrupt 0-3 Priority (PRI0)

4:0

Base 0xE000.E000 Offset 0x400 Type R/W, reset 0x0000.0000

	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16		
	,	INTD	•			reserved			INTC				reserved					
Туре	R/W	R/W	R/W	RO	RO	RO	RO	RO	R/W	R/W	R/W	RO	RO	RO	RO	RO		
Reset	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0		
r	15	14	13	12	11	10	9	8	7	6	5	4	3	2	1	0		
	,	INTB	•			reserved				INTA				reserved				
Туре	R/W	R/W	R/W 0	RO 0	RO 0	RO	RO	RO 0	R/W	R/W	R/W	RO 0	RO 0	RO	RO	RO		
Reset	0	0	U	U	U	0	0	U	0	0	0	U	U	0	0	0		
В	Bit/Field		Nam	ne	Ту	ре	Reset	Description										
	31:29		INT	D	R	W	0x0	Inte	rrupt Pric	ority for I	nterrupt	[4n+3]						
				_					•	•	•		or the int	terrupt wi	th the ni	ımber		
											•			Priority				
										,		the value	e, the gr	eater the	priority	of the		
								corr	espondir	ng interri	upt.							
28:24 reserved				R	0	0x0	Software should not rely on the value of a reserved bit. To p						. To prov	rovide				
										with future products, the value of a reserved bit should be								
								pres	preserved across a read-modify-write operation.									
	23:21		INT	С	R	W	0x0	Inte	Interrupt Priority for Interrupt [4n+2]									
								This field holds a priority value, 0-7, for the interrupt with										
								[4n+2], where n is the number of the Interrup PRI0 , and so on). The lower the value, the gr						• • •				
									espondir	,		uic value	s, the gr	cater tric	priority	or tile		
					_								_		_			
	20:16		reserv	ved	R	.O	0x0		Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be									
									preserved across a read-modify-write operation.									
	15:13		INT	D	D	W	0x0	Into	rrunt Driv	ority for I	nterrupt	[4n±1]						
	13.13		11111	Ь	IV.	VV	UXU		•	•	•		or the int	errunt wi	th tha ni	ımher		
							This field holds a priority value, 0-7, for the interrupt with the number [4n+1], where n is the number of the Interrupt Priority register (n=0 for											
								PRI	0 , and so	on). Th	ne lower t			eater the				
								corr	espondir	ng interru	upt.							
	12:8		reserv	ved	R	.O	0x0	Soft	ware sho	ould not	rely on th	he value	of a res	erved bit.	. To prov	ride		
														a reserv	ed bit sh	ould be		
								pres	served a	cross a r	ead-mod	aity-write	operation	on.				
	7:5		INT	Α	R	W	0x0	Inte	rrupt Pric	ority for I	nterrupt	[4n]						

RO

reserved

0x0

corresponding interrupt.

This field holds a priority value, 0-7, for the interrupt with the number [4n], where n is the number of the **Interrupt Priority** register (n=0 for PRIO, and so on). The lower the value, the greater the priority of the

Software should not rely on the value of a reserved bit. To provide

preserved across a read-modify-write operation.

compatibility with future products, the value of a reserved bit should be

Register 45: Interrupt 64-67 Priority (PRI16), offset 0x440 Register 46: Interrupt 68-71 Priority (PRI17), offset 0x444 Register 47: Interrupt 72-75 Priority (PRI18), offset 0x448 Register 48: Interrupt 76-79 Priority (PRI19), offset 0x44C Register 49: Interrupt 80-83 Priority (PRI20), offset 0x450 Register 50: Interrupt 84-87 Priority (PRI21), offset 0x454 Register 51: Interrupt 88-91 Priority (PRI22), offset 0x458 Register 52: Interrupt 92-95 Priority (PRI23), offset 0x45C Register 53: Interrupt 96-99 Priority (PRI24), offset 0x460 Register 54: Interrupt 100-103 Priority (PRI25), offset 0x464 Register 55: Interrupt 104-107 Priority (PRI26), offset 0x468 Register 56: Interrupt 108-111 Priority (PRI27), offset 0x46C Register 57: Interrupt 112-115 Priority (PRI28), offset 0x470 Register 58: Interrupt 116-119 Priority (PRI29), offset 0x474 Register 59: Interrupt 120-123 Priority (PRI30), offset 0x478 Register 60: Interrupt 124-127 Priority (PRI31), offset 0x47C Register 61: Interrupt 128-131 Priority (PRI32), offset 0x480 Register 62: Interrupt 132-135 Priority (PRI33), offset 0x484 Register 63: Interrupt 136-138 Priority (PRI34), offset 0x488

Note: This register can only be accessed from privileged mode.

The **PRIn** registers (see also page 156) provide 3-bit priority fields for each interrupt. These registers are byte accessible. Each register holds four priority fields that are assigned to interrupts as follows:

PRIn Register Bit Field	Interrupt
Bits 31:29	Interrupt [4n+3]
Bits 23:21	Interrupt [4n+2]
Bits 15:13	Interrupt [4n+1]
Bits 7:5	Interrupt [4n]

See Table 2-9 on page 108 for interrupt assignments.

Each priority level can be split into separate group priority and subpriority fields. The PRIGROUP field in the **Application Interrupt and Reset Control (APINT)** register (see page 168) indicates the position of the binary point that splits the priority and subpriority fields.

These registers can only be accessed from privileged mode.

Interrupt 64-67 Priority (PRI16)

Base 0xE000.E000 Offset 0x440 Type R/W, reset 0x0000.0000

туре	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16
	Ţ.	INTD				reserved	·			INTC	- '			reserved	.,	
Туре	R/W	R/W	R/W	RO	RO	RO	RO	RO	R/W	R/W	R/W	RO	RO	RO	RO	RO
Reset	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0
	15	14 INTB	13 I	12	11	10 reserved	9	8	7	6 INTA	5 I	4	3	2 reserved	1	0
Туре	R/W	R/W	R/W	RO	RO	RO	RO	RO	R/W	R/W	R/W	RO	RO	RO	RO	RO
Reset	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0
E	Bit/Field		Name Type		Reset	Des	cription									
	31:29		INT	D	R/	W	0x0	Inte	rrupt Prid	ority for I	nterrupt	[4n+3]				
	20.24			eserved RO		00	This field holds a priority value, 0-7, for the interrupt with the nu [4n+3], where n is the number of the Interrupt Priority register (PRIO , and so on). The lower the value, the greater the priority corresponding interrupt.								(n=0 for of the	
	28:24		reser	vea	K	.0	0x0	com	patibility	with fut	ure prod		value o	served bit. f a reserve on.		
	23:21		INT	С	R/	W	0x0	Inte	rrupt Prid	ority for I	nterrupt	[4n+2]				
								[4n+	-2], wher	e n is the on). Th	e numbe ne lower	r of the Ir	terrupt	terrupt wit t Priority reater the	egister	(n=0 for
	20:16		reserv	ved	RO		0x0	com	oftware should not rely on the value of a reserved bit. To provide impatibility with future products, the value of a reserved bit should eserved across a read-modify-write operation.							
	15:13		INT	В	R/	W	0x0	Inte	rrupt Pri	ority for I	nterrupt	[4n+1]				
								[4n+ PRI	-1], wher	e n is the o on). Th	e numbe ne lower	r of the Ir	terrupt	terrupt wit t Priority reater the	egister	(n=0 for
	12:8		reserv	ved	R	RO		com	ritware should not rely on the value of a reserved bit. To prepare the products, the value of a reserved be served across a read-modify-write operation.							
	7:5		INT	Α	R/	W	0x0	Inte	rrupt Pri	ority for I	nterrupt	[4n]				
								[4n] PRI	, where i	n is the roon). Th	number one lower	of the Int e	errupt F	terrupt wit Priority re eater the	gister (r	n=0 for
	4:0		reserv	ved	R	Ю.	0x0	com	patibility	with fut	ure prod		value o	served bit. f a reserve on.		

Register 64: Software Trigger Interrupt (SWTRIG), offset 0xF00

Note: Only privileged software can enable unprivileged access to the SWTRIG register.


Writing an interrupt number to the **SWTRIG** register generates a Software Generated Interrupt (SGI). See Table 2-9 on page 108 for interrupt assignments.

When the MAINPEND bit in the **Configuration and Control (CFGCTRL)** register (see page 172) is set, unprivileged software can access the **SWTRIG** register.

Software Trigger Interrupt (SWTRIG)

Base 0xE000.E000 Offset 0xF00

Type WO, reset 0x0000.0000



Bit/Field	Name	Type	Reset	Description
31:8	reserved	RO	0x0000.00	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
7:0	INTID	WO	0x00	Interrupt ID

This field holds the interrupt ID of the required SGI. For example, a value of 0x3 generates an interrupt on IRQ3.

3.5 System Control Block (SCB) Register Descriptions

This section lists and describes the System Control Block (SCB) registers, in numerical order by address offset. The SCB registers can only be accessed from privileged mode.

All registers must be accessed with aligned word accesses except for the **FAULTSTAT** and **SYSPRI1-SYSPRI3** registers, which can be accessed with byte or aligned halfword or word accesses. The processor does not support unaligned accesses to system control block registers.

Register 65: Auxiliary Control (ACTLR), offset 0x008


Note: This register can only be accessed from privileged mode.

The **ACTLR** register provides disable bits for IT folding, write buffer use for accesses to the default memory map, and interruption of multi-cycle instructions. By default, this register is set to provide optimum performance from the Cortex-M4 processor and does not normally require modification.

Auxiliary Control (ACTLR)

Base 0xE000.E000 Offset 0x008

Type R/W, reset 0x0000.0000



Bit/Field	Name	Type	Reset	Description
31:10	reserved	RO	0x00	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
9	DISOOFP	R/W	0	Disable Out-Of-Order Floating Point
				Disables floating-point instructions completing out of order with respect to integer instructions.
8	DISFPCA	R/W	0	Disable CONTROL.FPCA
				Disable automatic update of the FPCA bit in the CONTROL register.
				Important: Two bits control when FPCA can be enabled: the ASPEN bit in the Floating-Point Context Control (FPCC) register and the DISFPCA bit in the Auxiliary Control (ACTLR) register.
7:3	reserved	RO	0x00	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
2	DISFOLD	R/W	0	Disable IT Folding
				Value Description

In some situations, the processor can start executing the first instruction in an ${\tt IT}$ block while it is still executing the ${\tt IT}$ instruction. This behavior is called ${\it IT}$ folding, and improves performance, However, ${\tt IT}$ folding can cause jitter in looping. If a task must avoid jitter, set the ${\tt DISFOLD}$ bit before executing the task, to disable ${\tt IT}$ folding.

0

1

No effect.

Disables IT folding.

Bit/Field	Name	Type	Reset	Description
1	DISWBUF	R/W	0	Disable Write Buffer
				Value Description
				0 No effect.
				Disables write buffer use during default memory map accesses. In this situation, all bus faults are precise bus faults but performance is decreased because any store to memory must complete before the processor can execute the next instruction.
				Note: This bit only affects write buffers implemented in the Cortex-M4 processor.
0	DISMCYC	R/W	0	Disable Interrupts of Multiple Cycle Instructions
				Value Description
				0 No effect.
				1 Disables interruption of load multiple and store multiple

instructions. In this situation, the interrupt latency of the processor is increased because any ${\tt LDM}$ or ${\tt STM}$ must complete before the processor can stack the current state and enter the

interrupt handler.

Register 66: CPU ID Base (CPUID), offset 0xD00

Note: This register can only be accessed from privileged mode.

The CPUID register contains the ARM® Cortex™-M4 processor part number, version, and implementation information.

CPU ID Base (CPUID)

Base 0xE000.E000


3:0

REV

RO

0x1

Offset 0xD00 Type RO, reset 0x410F.C241



Value Description

Revision Number

0xC24 Cortex-M4 processor.

The pn value in the rnpn product revision identifier, for example, the 1 in r0p1.

Register 67: Interrupt Control and State (INTCTRL), offset 0xD04

Note: This register can only be accessed from privileged mode.

The **INCTRL** register provides a set-pending bit for the NMI exception, and set-pending and clear-pending bits for the PendSV and SysTick exceptions. In addition, bits in this register indicate the exception number of the exception being processed, whether there are preempted active exceptions, the exception number of the highest priority pending exception, and whether any interrupts are pending.


When writing to **INCTRL**, the effect is unpredictable when writing a 1 to both the PENDSV and UNPENDSV bits, or writing a 1 to both the PENDSTSET and PENDSTCLR bits.

Interrupt Control and State (INTCTRL)

Base 0xE000.E000 Offset 0xD04

28

Type R/W, reset 0x0000.0000



Bit/Field	Name	Туре	Reset	Description	
31	NMISET	R/W	0	NMI Set Pendir	ıq

R/W

n

Value Description

- On a read, indicates an NMI exception is not pending. On a write, no effect.
- On a read, indicates an NMI exception is pending.
 On a write, changes the NMI exception state to pending.

Because NMI is the highest-priority exception, normally the processor enters the NMI exception handler as soon as it registers the setting of this bit, and clears this bit on entering the interrupt handler. A read of this bit by the NMI exception handler returns 1 only if the NMI signal is reasserted while the processor is executing that handler.

30:29	reserved	RO	0x0

PENDSV

Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.

PendSV Set Pending

Value Description

- On a read, indicates a PendSV exception is not pending.
 On a write, no effect.
- On a read, indicates a PendSV exception is pending.
 On a write, changes the PendSV exception state to pending.

Setting this bit is the only way to set the PendSV exception state to pending. This bit is cleared by writing a 1 to the ${\tt UNPENDSV}$ bit.

Bit/Field	Name	Туре	Reset	Description
27	UNPENDSV	WO	0	PendSV Clear Pending
				Value Description
				0 On a write, no effect.
				On a write, removes the pending state from the PendSV exception.
				This bit is write only; on a register read, its value is unknown.
26	PENDSTSET	R/W	0	SysTick Set Pending
				Value Description
				 On a read, indicates a SysTick exception is not pending. On a write, no effect.
				1 On a read, indicates a SysTick exception is pending.
				On a write, changes the SysTick exception state to pending.
				This bit is cleared by writing a 1 to the PENDSTCLR bit.
25	PENDSTCLR	WO	0	SysTick Clear Pending
				Value Description
				0 On a write, no effect.
				On a write, removes the pending state from the SysTick exception.
				This bit is write only; on a register read, its value is unknown.
24	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
23	ISRPRE	RO	0	Debug Interrupt Handling
				Value Description
				O The release from halt does not take an interrupt.
				1 The release from halt takes an interrupt.
				This bit is only meaningful in Debug mode and reads as zero when the processor is not in Debug mode.
22	ISRPEND	RO	0	Interrupt Pending
				Value Description
				0 No interrupt is pending.
				1 An interrupt is pending.
				This bit provides status for all interrupts excluding NMI and Faults.
21:20	reserved	RO	0x0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.

February 20, 2013 165

Bit/Field	Name	Туре	Reset	Description
19:12	VECPEND	RO	0x00	Interrupt Pending Vector Number This field contains the exception number of the highest priority pending enabled exception. The value indicated by this field includes the effect of the BASEPRI and FAULTMASK registers, but not any effect of the PRIMASK register.
				Value Description
				0x00 No exceptions are pending
				0x01 Reserved
				0x02 NMI
				0x03 Hard fault
				0x04 Memory management fault
				0x05 Bus fault
				0x06 Usage fault
				0x07-0x0A Reserved
				0x0B SVCall
				0x0C Reserved for Debug
				0x0D Reserved
				0x0E PendSV
				0x0F SysTick
				0x10 Interrupt Vector 0
				'
				0x9A Interrupt Vector 138
				'
				0x94-0x7F Reserved
11	RETBASE	RO	0	Return to Base
				Value Description
				O There are preempted active exceptions to execute.
				1 There are no active exceptions, or the currently executing exception is the only active exception.
				This bit provides status for all interrupts excluding NMI and Faults. This bit only has meaning if the processor is currently executing an ISR (the Interrupt Program Status (IPSR) register is non-zero).
10:8	reserved	RO	0x0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
7:0	VECACT	RO	0x00	Interrupt Pending Vector Number
				This field contains the active exception number. The exception numbers can be found in the description for the VECPEND field. If this field is clear, the processor is in Thread mode. This field contains the same value as the ISRNUM field in the IPSR register.
				Subtract 16 from this value to obtain the IRQ number required to index into the Interrupt Set Enable (ENn), Interrupt Clear Enable (DISn), Interrupt Set Pending (PENDn), Interrupt Clear Pending (UNPENDn), and Interrupt Priority (PRIn) registers (see page 85).

Register 68: Vector Table Offset (VTABLE), offset 0xD08

Note: This register can only be accessed from privileged mode.

The **VTABLE** register indicates the offset of the vector table base address from memory address 0x0000.0000.

Vector Table Offset (VTABLE)

Base 0xE000.E000 Offset 0xD08

Offse	t 0xD08 R/W, res		0.0000													
	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16
	rese	rved	BASE			ı				OFFSET	•			ı	ı	'
Type Reset	RO 0	RO 0	R/W 0	R/W 0	R/W 0	R/W 0	R/W 0	R/W 0	R/W 0	R/W 0						
	15	14	13	12	11	10	9	8	7	6	5	4	3	2	1	0
			OFF	SET		ı	1				rese	rved	1	ì	ĺ	
Type Reset	R/W 0	R/W 0	R/W 0	R/W 0	R/W 0	R/W 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0
Е	Bit/Field		Nam	ne	Ту	ре	Reset	Des	cription							
	31:30		reserv	/ed	R	0	0x0	com	patibility	with fut	rely on to ure produ ead-mod	ucts, the	value of	a reserv		
	29		BAS	E	R	W	0	Vec	tor Table	Base						
								Vali	ue Desc	ription						
								0	The	vector ta	ble is in	the code	memor	y region.		
								1	The	vector ta	ble is in	the SRA	M memo	ory regio	n.	
	28:10		OFFS	ET	R	W	0x000.00	Vec	tor Table	Offset						
								num	ber of ex	xception	e OFFSE' entries i must be	n the ve	ctor table	e. Becau	se there	are 138
	9:0		reserv	/ed	R	0	0x00	com	patibility	with fut	rely on thure produced	ucts, the	value of	a reserv		

Register 69: Application Interrupt and Reset Control (APINT), offset 0xD0C

Note: This register can only be accessed from privileged mode.

The **APINT** register provides priority grouping control for the exception model, endian status for data accesses, and reset control of the system. To write to this register, 0x05FA must be written to the VECTKEY field, otherwise the write is ignored.

The PRIGROUP field indicates the position of the binary point that splits the INTx fields in the Interrupt Priority (PRIx) registers into separate group priority and subpriority fields. Table 3-9 on page 168 shows how the PRIGROUP value controls this split. The bit numbers in the Group Priority Field and Subpriority Field columns in the table refer to the bits in the INTA field. For the INTB field, the corresponding bits are 15:13; for INTC, 23:21; and for INTD, 31:29.

Note: Determining preemption of an exception uses only the group priority field.

Table 3-9. Interrupt Priority Levels


PRIGROUP Bit Field	Binary Point ^a	Group Priority Field		Group Priorities	Subpriorities
0x0 - 0x4	bxxx.	[7:5]	None	8	1
0x5	bxx.y	[7:6]	[5]	4	2
0x6	bx.yy	[7]	[6:5]	2	4
0x7	b.yyy	None	[7:5]	1	8

a. INTx field showing the binary point. An x denotes a group priority field bit, and a y denotes a subpriority field bit.

Application Interrupt and Reset Control (APINT)

Base 0xE000.E000 Offset 0xD0C

Type R/W, reset 0xFA05.0000



Bit/Field	Name	Type	Reset	Description
31:16	VECTKEY	R/W	0xFA05	Register Key
				This field is used to guard against accidental writes to this register. 0x05FA must be written to this field in order to change the bits in this register. On a read, 0xFA05 is returned.
15	ENDIANESS	RO	0	Data Endianess
				The Stellaris implementation uses only little-endian mode so this is cleared to $\boldsymbol{0}.$
14:11	reserved	RO	0x0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.

Bit/Field	Name	Туре	Reset	Description				
10:8	PRIGROUP	R/W	0x0	Interrupt Priority Grouping This field determines the split of group priority from subpriority (see Table 3-9 on page 168 for more information).				
7:3	reserved	RO	0x0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should preserved across a read-modify-write operation.				
2	SYSRESREQ	WO	0	System Reset Request				
				Value Description				
				0 No effect.				
				1 Resets the core and all on-chip peripherals except the Debug interface.				
				This bit is automatically cleared during the reset of the core and reads as 0.				
1	VECTCLRACT	WO	0	Clear Active NMI / Fault				
				This bit is reserved for Debug use and reads as 0. This bit must be written as a 0, otherwise behavior is unpredictable.				
0	VECTRESET	WO	0	System Reset				
				This bit is reserved for Debug use and reads as 0. This bit must be written as a 0, otherwise behavior is unpredictable.				

Register 70: System Control (SYSCTRL), offset 0xD10

Note: This register can only be accessed from privileged mode.

The SYSCTRL register controls features of entry to and exit from low-power state.

System Control (SYSCTRL)

Base 0xE000.E000

Offset 0xD10
Type R/W, reset 0x0000.0000

	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16
		1	1	1				rese	rved	,		1 1				
								ŗ								
Туре	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO
Reset	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0
	15	14	13	12	11	10	9	8	7	6	5	4	3	2	1	0
		1	1			reserved						SEVONPEND		01 5500550	OI EEDEWIT	**************************************
						reserved						SEVUNPEND	reserved	SLEEPDEEP	SLEEPEXII	reserved
Туре	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	R/W	RO	R/W	R/W	RO
		110	NO	RU	RU	NO	KO.	NO	RU	RU	RU	R/VV	RU	FX/VV	17/44	110
Reset	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0
Reset	0															
Reset	0															
			0	0	0	0	0	0	0							
	o Bit/Field			0		0		0								

31:5	reserved	RO	0x0000.00	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
4	SEVONPEND	R/W	0	Wake Up on Pending

Value Description

- Only enabled interrupts or events can wake up the processor; disabled interrupts are excluded.
- 1 Enabled events and all interrupts, including disabled interrupts, can wake up the processor.

When an event or interrupt enters the pending state, the event signal wakes up the processor from $\mathtt{WFE}.$ If the processor is not waiting for an event, the event is registered and affects the next WFE.

The processor also wakes up on execution of a SEV instruction or an external event.

3	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
2	SLEEPDEEP	R/W	0	Deep Sleep Enable

Value Description

- Use Sleep mode as the low power mode.
- Use Deep-sleep mode as the low power mode.

Bit/Field	Name	Туре	Reset	Description
1	SLEEPEXIT	R/W	0	Sleep on ISR Exit
				Value Description
				When returning from Handler mode to Thread mode, do not sleep when returning to Thread mode.
				When returning from Handler mode to Thread mode, enter sleep or deep sleep on return from an ISR.
				Setting this bit enables an interrupt-driven application to avoid returning to an empty main application.
0	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.

Register 71: Configuration and Control (CFGCTRL), offset 0xD14


Note: This register can only be accessed from privileged mode.

The **CFGCTRL** register controls entry to Thread mode and enables: the handlers for NMI, hard fault and faults escalated by the **FAULTMASK** register to ignore bus faults; trapping of divide by zero and unaligned accesses; and access to the **SWTRIG** register by unprivileged software (see page 160).

Configuration and Control (CFGCTRL)

Base 0xE000.E000 Offset 0xD14

Type R/W, reset 0x0000.0200



Bit/Field	Name	Type	Reset	Description
31:10	reserved	RO	0x0000.00	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
9	STKALIGN	R/W	1	Stack Alignment on Exception Entry
				Value Description
				0 The stack is 4-byte aligned.
				1 The stack is 8-byte aligned.
				On exception entry, the processor uses bit 9 of the stacked PSR to indicate the stack alignment. On return from the exception, it uses this stacked bit to restore the correct stack alignment.
8	BFHFNMIGN	R/W	0	Ignore Bus Fault in NMI and Fault
				This bit enables handlers with priority -1 or -2 to ignore data bus faults caused by load and store instructions. The setting of this bit applies to the hard fault, NMI, and FAULTMASK escalated handlers.
				Value Description
				0 Data bus faults caused by load and store instructions cause a lock-up.
				1 Handlers running at priority -1 and -2 ignore data bus faults caused by load and store instructions.
				Set this bit only when the handler and its data are in absolutely safe memory. The normal use of this bit is to probe system devices and bridges to detect control path problems and fix them.
7:5	reserved	RO	0x0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.

Bit/Field	Name	Type	Reset	Description
4	DIV0	R/W	0	Trap on Divide by 0
				This bit enables faulting or halting when the processor executes an SDIV or UDIV instruction with a divisor of 0.
				Value Description
				O Do not trap on divide by 0. A divide by zero returns a quotient of 0.
				1 Trap on divide by 0.
3	UNALIGNED	R/W	0	Trap on Unaligned Access
				Value Description
				0 Do not trap on unaligned halfword and word accesses.
				1 Trap on unaligned halfword and word accesses. An unaligned access generates a usage fault.
				Unaligned LDM, STM, LDRD, and STRD instructions always fault regardless of whether UNALIGNED is set.
2	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
1	MAINPEND	R/W	0	Allow Main Interrupt Trigger
				Value Description
				0 Disables unprivileged software access to the SWTRIG register.
				1 Enables unprivileged software access to the SWTRIG register (see page 160).
0	BASETHR	R/W	0	Thread State Control
				Value Description
				The processor can enter Thread mode only when no exception is active.
				The processor can enter Thread mode from any level under the control of an EXC_RETURN value (see "Exception Return" on page 114 for more information).

February 20, 2013 173

Register 72: System Handler Priority 1 (SYSPRI1), offset 0xD18

Note: This register can only be accessed from privileged mode.

The SYSPRI1 register configures the priority level, 0 to 7 of the usage fault, bus fault, and memory management fault exception handlers. This register is byte-accessible.

System Handler Priority 1 (SYSPRI1)

Base 0xE000.E000 Offset 0xD18 Type R/W, reset 0x0000.0000

4:0

71	,															
	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16
	'		1	rese	rved		, ,			USAGE				reserved		•
Туре	RO	RO	RO	RO	RO	RO	RO	RO	R/W	R/W	R/W	RO	RO	RO	RO	RO
Reset	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0
	15	14	13	12	11	10	9	8	7	6	5	4	3	2	1	0
	•	BUS	•			reserved	'			MEM				reserved		'
Туре	R/W	R/W	R/W	RO	RO	RO	RO	RO	R/W	R/W	R/W	RO	RO	RO	RO	RO
Reset	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0
							_									
Е	Bit/Field		Nan	ne	Ту	pe	Reset	Des	cription							
	31:24		reser	ved	R	0	0x00	Soft	ware sh	ould not i	ely on t	he value	of a res	erved bit.	To prov	/ide
										with futu					ed bit sh	nould be
								pres	served a	cross a re	ead-mod	dify-write	operation	on.		
	23:21		USA	GE	R/	W	0x0	Usa	ge Fault	Priority						
								This	s field co	nfigures	the prior	ity level	of the us	age fault	. Config	urable
									•	es are in	the rang	je 0-7, wi	ith lower	values h	aving h	igher
								prio	rity.							
	20:16		reser	ved	R	0	0x0	Soft	ware sh	ould not i	ely on t	he value	of a res	erved bit.	To prov	/ide
										with futu	•				ed bit sh	nould be
								pres	served a	cross a re	ead-mod	dify-write	operation	on.		
	15:13		BU	S	R/	W	0x0	Bus	Fault P	riority						
								This	field cor	nfigures th	ne priorit	y level of	the bus	fault. Con	figurable	e priority
								valu	ies are ii	n the rang	ge 0-7, v	with lowe	r values	having h	igher pr	iority.
	12:8		reser	ved	R	0	0x0	Soft	ware sh	ould not i	elv on t	he value	of a res	erved bit.	To prov	/ide
								com	patibility	with futu	ire prod	ucts, the	value of	a reserv		
								pres	served a	cross a re	ead-mod	dify-write	operation	n.		
	7:5		MEI	М	R/	W	0x0	Mer	nory Ma	nagemer	ıt Fault f	Priority				
								This	field co	nfigures t	he prior	ity level c	of the me	mory ma	nageme	ent fault.
									-	e priority		are in the	range 0	-7, with l	ower va	lues
								havi	ing nighe	er priority	•					
					_	_							_		_	

Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be

preserved across a read-modify-write operation.

RO

reserved

0x0

Register 73: System Handler Priority 2 (SYSPRI2), offset 0xD1C


Note: This register can only be accessed from privileged mode.

The SYSPRI2 register configures the priority level, 0 to 7 of the SVCall handler. This register is byte-accessible.

System Handler Priority 2 (SYSPRI2)

Base 0xE000.E000

Offset 0xD1C Type R/W, reset 0x0000.0000



31:29 SVC R/W 0x0 **SVCall Priority**

> This field configures the priority level of SVCall. Configurable priority values are in the range 0-7, with lower values having higher priority.

28:0 RO 0x000.0000 reserved

Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.

Register 74: System Handler Priority 3 (SYSPRI3), offset 0xD20

Note: This register can only be accessed from privileged mode.


The SYSPRI3 register configures the priority level, 0 to 7 of the SysTick exception and PendSV handlers. This register is byte-accessible.

System Handler Priority 3 (SYSPRI3)

reserved

Base 0xE000.E000 Offset 0xD20

Type R/W, reset 0x0000.0000



compatibility with future products, the value of a reserved bit should be

preserved across a read-modify-write operation.

Register 75: System Handler Control and State (SYSHNDCTRL), offset 0xD24

Note: This register can only be accessed from privileged mode.

The **SYSHNDCTRL** register enables the system handlers, and indicates the pending status of the usage fault, bus fault, memory management fault, and SVC exceptions as well as the active status of the system handlers.

If a system handler is disabled and the corresponding fault occurs, the processor treats the fault as a hard fault.

This register can be modified to change the pending or active status of system exceptions. An OS kernel can write to the active bits to perform a context switch that changes the current exception type.


Caution – Software that changes the value of an active bit in this register without correct adjustment to the stacked content can cause the processor to generate a fault exception. Ensure software that writes to this register retains and subsequently restores the current active status.

If the value of a bit in this register must be modified after enabling the system handlers, a read-modify-write procedure must be used to ensure that only the required bit is modified.

System Handler Control and State (SYSHNDCTRL)

Base 0xE000.E000 Offset 0xD24

Type R/W, reset 0x0000.0000



Bit/Field	Name	Туре	Reset	Description			
31:19	reserved	RO	0x000	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.			
18	USAGE	R/W	0	Usage Fault Enable			
				Value Description			
				0 Disables the usage fault exception.			
				1 Enables the usage fault exception.			
17	BUS	R/W	0	Bus Fault Enable			
				Value Description			
				O Disables the bus fault exception.			

Enables the bus fault exception.

Bit/Field	Name	Туре	Reset	Description
16	MEM	R/W	0	Memory Management Fault Enable
				 Value Description Disables the memory management fault exception. Enables the memory management fault exception.
15	SVC	R/W	0	SVC Call Pending Value Description 0 An SVC call exception is not pending.
				An SVC call exception is pending. This bit can be modified to change the pending status of the SVC call exception.
14	BUSP	R/W	0	Bus Fault Pending
				Value Description O A bus fault exception is not pending. A bus fault exception is pending.
				This bit can be modified to change the pending status of the bus fault exception.
13	MEMP	R/W	0	Memory Management Fault Pending
				Value Description O A memory management fault exception is not pending. A memory management fault exception is pending. This bit can be modified to change the pending status of the memory management fault exception.
12	USAGEP	R/W	0	Usage Fault Pending
				Value Description O A usage fault exception is not pending. A usage fault exception is pending. This bit can be modified to change the pending status of the usage fault exception.
11	TICK	R/W	0	SysTick Exception Active Value Description 0 A SysTick exception is not active. 1 A SysTick exception is active. This bit can be modified to change the active status of the SysTick exception, however, see the Caution above before setting this bit.

Bit/Field	Name	Туре	Reset	Description
10	PNDSV	R/W	0	PendSV Exception Active
				Value Description
				0 A PendSV exception is not active.
				1 A PendSV exception is active.
				This bit can be modified to change the active status of the PendSV exception, however, see the Caution above before setting this bit.
9	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
8	MON	R/W	0	Debug Monitor Active
				Value Description
				0 The Debug monitor is not active.
				1 The Debug monitor is active.
7	SVCA	R/W	0	SVC Call Active
				Value Description
				0 SVC call is not active.
				1 SVC call is active.
				This bit can be modified to change the active status of the SVC call exception, however, see the Caution above before setting this bit.
6:4	reserved	RO	0x0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
3	USGA	R/W	0	Usage Fault Active
				Value Description
				0 Usage fault is not active.
				1 Usage fault is active.
				This bit can be modified to change the active status of the usage fault exception, however, see the Caution above before setting this bit.
2	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
1	BUSA	R/W	0	Bus Fault Active
				Value Description
				0 Bus fault is not active.
				1 Bus fault is active.
				This bit can be modified to change the active status of the bus fault exception, however, see the Caution above before setting this bit.

February 20, 2013 179

Bit/Field	Name	Туре	Reset	Description
0	MEMA	R/W	0	Memory Management Fault Active
				Value Description 0 Memory management fault is not active. 1 Memory management fault is active. This bit can be modified to change the active status of the memory management fault exception, however, see the Caution above before setting this bit.

Register 76: Configurable Fault Status (FAULTSTAT), offset 0xD28

Note: This register can only be accessed from privileged mode.

The **FAULTSTAT** register indicates the cause of a memory management fault, bus fault, or usage fault. Each of these functions is assigned to a subregister as follows:

- Usage Fault Status (UFAULTSTAT), bits 31:16
- Bus Fault Status (BFAULTSTAT), bits 15:8
- Memory Management Fault Status (MFAULTSTAT), bits 7:0

FAULTSTAT is byte accessible. FAULTSTAT or its subregisters can be accessed as follows:

- The complete **FAULTSTAT** register, with a word access to offset 0xD28
- The **MFAULTSTAT**, with a byte access to offset 0xD28
- The MFAULTSTAT and BFAULTSTAT, with a halfword access to offset 0xD28
- The **BFAULTSTAT**, with a byte access to offset 0xD29
- The **UFAULTSTAT**, with a halfword access to offset 0xD2A

Bits are cleared by writing a 1 to them.

In a fault handler, the true faulting address can be determined by:


- Read and save the Memory Management Fault Address (MMADDR) or Bus Fault Address (FAULTADDR) value.
- 2. Read the MMARV bit in MFAULTSTAT, or the BFARV bit in BFAULTSTAT to determine if the MMADDR or FAULTADDR contents are valid.

Software must follow this sequence because another higher priority exception might change the **MMADDR** or **FAULTADDR** value. For example, if a higher priority handler preempts the current fault handler, the other fault might change the **MMADDR** or **FAULTADDR** value.

Configurable Fault Status (FAULTSTAT)

Base 0xE000.E000 Offset 0xD28

Type R/W1C, reset 0x0000.0000



Bit/Field	Name	Туре	Reset	Description
25	DIV0	R/W1C	0	Divide-by-Zero Usage Fault
				Value Description
				No divide-by-zero fault has occurred, or divide-by-zero trapping is not enabled.
				1 The processor has executed an SDIV or UDIV instruction with a divisor of 0.
				When this bit is set, the PC value stacked for the exception return points to the instruction that performed the divide by zero.
				Trapping on divide-by-zero is enabled by setting the DIVO bit in the Configuration and Control (CFGCTRL) register (see page 172).
				This bit is cleared by writing a 1 to it.
24	UNALIGN	R/W1C	0	Unaligned Access Usage Fault
				Value Description
				No unaligned access fault has occurred, or unaligned access trapping is not enabled.
				1 The processor has made an unaligned memory access.
				Unaligned LDM, STM, LDRD, and STRD instructions always fault regardless of the configuration of this bit.
				Trapping on unaligned access is enabled by setting the UNALIGNED bit in the CFGCTRL register (see page 172).
				This bit is cleared by writing a 1 to it.
23:20	reserved	RO	0x00	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
19	NOCP	R/W1C	0	No Coprocessor Usage Fault
				Value Description
				O A usage fault has not been caused by attempting to access a coprocessor.
				1 The processor has attempted to access a coprocessor.
				This bit is cleared by writing a 1 to it.
18	INVPC	R/W1C	0	Invalid PC Load Usage Fault
				Value Description
				O A usage fault has not been caused by attempting to load an invalid PC value.
				The processor has attempted an illegal load of EXC_RETURN to the PC as a result of an invalid context or an invalid EXC_RETURN value.
				When this bit is set, the PC value stacked for the exception return points to the instruction that tried to perform the illegal load of the PC .
				This bit is cleared by writing a 1 to it.

Bit/Field	Name	Туре	Reset	Description
17	INVSTAT	R/W1C	0	Invalid State Usage Fault
				Value Description
				O A usage fault has not been caused by an invalid state.
				1 The processor has attempted to execute an instruction that makes illegal use of the EPSR register.
				When this bit is set, the PC value stacked for the exception return points to the instruction that attempted the illegal use of the Execution Program Status Register (EPSR) register.
				This bit is not set if an undefined instruction uses the EPSR register.
				This bit is cleared by writing a 1 to it.
16	UNDEF	R/W1C	0	Undefined Instruction Usage Fault
				Value Description
				O A usage fault has not been caused by an undefined instruction.
				1 The processor has attempted to execute an undefined instruction.
				When this bit is set, the PC value stacked for the exception return points to the undefined instruction.
				An undefined instruction is an instruction that the processor cannot decode.
				This bit is cleared by writing a 1 to it.
15	BFARV	R/W1C	0	Bus Fault Address Register Valid
				Value Description
				The value in the Bus Fault Address (FAULTADDR) register is not a valid fault address.
				1 The FAULTADDR register is holding a valid fault address.
				This bit is set after a bus fault, where the address is known. Other faults can clear this bit, such as a memory management fault occurring later.
				If a bus fault occurs and is escalated to a hard fault because of priority, the hard fault handler must clear this bit. This action prevents problems if returning to a stacked active bus fault handler whose FAULTADDR register value has been overwritten.
				This bit is cleared by writing a 1 to it.
14	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
13	BLSPERR	R/W1C	0	Bus Fault on Floating-Point Lazy State Preservation
				Value Description
				No bus fault has occurred during floating-point lazy state preservation.
				A bus fault has occurred during floating-point lazy state preservation.
				This bit is cleared by writing a 1 to it.

February 20, 2013 183

Bit/Field	Name	Туре	Reset	Description
12	BSTKE	R/W1C	0	Stack Bus Fault
				Value Description No bus fault has occurred on stacking for exception entry. Stacking for an exception entry has caused one or more bus faults.
				When this bit is set, the SP is still adjusted but the values in the context area on the stack might be incorrect. A fault address is not written to the FAULTADDR register. This bit is cleared by writing a 1 to it.
11	DUCTIZE	DAM4C	0	, Ç
11	BUSTKE	R/W1C	0	Unstack Bus Fault
				Value Description
				 No bus fault has occurred on unstacking for a return from exception.
				1 Unstacking for a return from exception has caused one or more bus faults.
				This fault is chained to the handler. Thus, when this bit is set, the original return stack is still present. The SP is not adjusted from the failing return, a new save is not performed, and a fault address is not written to the FAULTADDR register.
				This bit is cleared by writing a 1 to it.
10	IMPRE	R/W1C	0	Imprecise Data Bus Error
				Value Description
				O An imprecise data bus error has not occurred.
				A data bus error has occurred, but the return address in the stack frame is not related to the instruction that caused the error.
				When this bit is set, a fault address is not written to the FAULTADDR register.
				This fault is asynchronous. Therefore, if the fault is detected when the priority of the current process is higher than the bus fault priority, the bus fault becomes pending and becomes active only when the processor returns from all higher-priority processes. If a precise fault occurs before the processor enters the handler for the imprecise bus fault, the handler detects that both the IMPRE bit is set and one of the precise fault status bits is set.
				This bit is cleared by writing a 1 to it.
9	PRECISE	R/W1C	0	Precise Data Bus Error
				Value Description
				O A precise data bus error has not occurred.
				A data bus error has occurred, and the PC value stacked for the exception return points to the instruction that caused the fault.
				When this bit is set, the fault address is written to the FAULTADDR register.
				This bit is also and becomition and the it

184 February 20, 2013

This bit is cleared by writing a 1 to it.

Bit/Field	Name	Туре	Reset	Description
8	IBUS	R/W1C	0	Instruction Bus Error
				Value Description
				O An instruction bus error has not occurred.
				1 An instruction bus error has occurred.
				The processor detects the instruction bus error on prefetching an instruction, but sets this bit only if it attempts to issue the faulting instruction.
				When this bit is set, a fault address is not written to the FAULTADDR register.
				This bit is cleared by writing a 1 to it.
7	MMARV	R/W1C	0	Memory Management Fault Address Register Valid
				Value Description
				The value in the Memory Management Fault Address (MMADDR) register is not a valid fault address.
				1 The MMADDR register is holding a valid fault address.
				If a memory management fault occurs and is escalated to a hard fault because of priority, the hard fault handler must clear this bit. This action prevents problems if returning to a stacked active memory management fault handler whose MMADDR register value has been overwritten.
				This bit is cleared by writing a 1 to it.
6	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
5	MLSPERR	R/W1C	0	Memory Management Fault on Floating-Point Lazy State Preservation
				Value Description
				No memory management fault has occurred during floating-point lazy state preservation.
				 No memory management fault has occurred during floating-point lazy state preservation.
				This bit is cleared by writing a 1 to it.
4	MSTKE	R/W1C	0	Stack Access Violation
				Value Description
				No memory management fault has occurred on stacking for exception entry.
				Stacking for an exception entry has caused one or more access violations.
				When this bit is set, the SP is still adjusted but the values in the context area on the stack might be incorrect. A fault address is not written to the MMADDR register.
				This bit is cleared by writing a 1 to it.

February 20, 2013 185

Bit/Field	Name	Туре	Reset	Description
3	MUSTKE	R/W1C	0	Unstack Access Violation
				Value Description
				No memory management fault has occurred on unstacking for a return from exception.
				1 Unstacking for a return from exception has caused one or more access violations.
				This fault is chained to the handler. Thus, when this bit is set, the original return stack is still present. The SP is not adjusted from the failing return, a new save is not performed, and a fault address is not written to the MMADDR register.
				This bit is cleared by writing a 1 to it.
2	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
1	DERR	R/W1C	0	Data Access Violation
				Value Description
				0 A data access violation has not occurred.
				1 The processor attempted a load or store at a location that does not permit the operation.
				When this bit is set, the PC value stacked for the exception return points to the faulting instruction and the address of the attempted access is written to the MMADDR register.
				This bit is cleared by writing a 1 to it.
0	IERR	R/W1C	0	Instruction Access Violation
				Value Description
				O An instruction access violation has not occurred.
				1 The processor attempted an instruction fetch from a location that does not permit execution.
				This fault occurs on any access to an XN region, even when the MPU is disabled or not present.
				When this bit is set, the PC value stacked for the exception return points to the faulting instruction and the address of the attempted access is not written to the MMADDR register.

This bit is cleared by writing a 1 to it.

Register 77: Hard Fault Status (HFAULTSTAT), offset 0xD2C

Note: This register can only be accessed from privileged mode.

The **HFAULTSTAT** register gives information about events that activate the hard fault handler.

Bits are cleared by writing a 1 to them.

Hard Fault Status (HFAULTSTAT)

Base 0xE000.E000

Offset 0xD2C Type R/W1C, reset 0x0000.0000

	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16
	DBG	FORCED					' '		rese	rved					•	ı
Type Reset	R/W1C 0	R/W1C 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0						
	15	14	13	12	11	10	9	8	7	6	5	4	3	2	1	0
		1					reser	ved							VECT	reserved
Type Reset	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	R/W1C 0	RO 0
E	Bit/Field		Nam	ne	Ту	ре	Reset	Des	cription							
	31		DBC	3	R/W	/1C	0	Deb	ug Even	t						
									bit is reservise be			•	is bit mu	ıst be wr	ritten as	a 0,
	30		FORC	ED	R/W	/1C	0	Ford	ed Hard	Fault						
								Valu	ue Desc	ription						
								0			rd fault h	as occur	rred.			
								1	with o	onfigura	ıble prior		annot be		alation o I, either b	
									en this bi					st read t	he other	fault
								This	bit is cle	ared by	writing a	a 1 to it.				
	29:2		reserv	/ed	R	0	0x00	com	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should preserved across a read-modify-write operation.							
	1		VEC	т	R/W	/1C	0	Vect	or Table	Read Fa	ault					
								Valu	ue Desc	ription						
								0			nas occu	rred on a	a vector	table rea	ad.	
								1	A bus	s fault oc	curred c	n a vect	or table	read.		
								This	error is	always h	nandled l	by the ha	ard fault	handler.		
									en this bit e instruc	-					tion retur า.	n points
								This	bit is cle	ared by	writing a	a 1 to it.				
	0		reserv	/ed	R	0	0	com		with futu	ıre produ	ucts, the	value of	a reserv	t. To prov ved bit sh	


Register 78: Memory Management Fault Address (MMADDR), offset 0xD34

Note: This register can only be accessed from privileged mode.

The MMADDR register contains the address of the location that generated a memory management fault. When an unaligned access faults, the address in the MMADDR register is the actual address that faulted. Because a single read or write instruction can be split into multiple aligned accesses, the fault address can be any address in the range of the requested access size. Bits in the Memory Management Fault Status (MFAULTSTAT) register indicate the cause of the fault and whether the value in the MMADDR register is valid (see page 181).

Memory Management Fault Address (MMADDR)

Base 0xE000.E000 Offset 0xD34 Type R/W, reset -




When the MMARV bit of **MFAULTSTAT** is set, this field holds the address of the location that generated the memory management fault.


Register 79: Bus Fault Address (FAULTADDR), offset 0xD38

Note: This register can only be accessed from privileged mode.

The **FAULTADDR** register contains the address of the location that generated a bus fault. When an unaligned access faults, the address in the **FAULTADDR** register is the one requested by the instruction, even if it is not the address of the fault. Bits in the **Bus Fault Status (BFAULTSTAT)** register indicate the cause of the fault and whether the value in the **FAULTADDR** register is valid (see page 181).



Base 0xE000.E000 Offset 0xD38 Type R/W, reset -



When the FAULTADDRV bit of **BFAULTSTAT** is set, this field holds the address of the location that generated the bus fault.

3.6 Memory Protection Unit (MPU) Register Descriptions

This section lists and describes the Memory Protection Unit (MPU) registers, in numerical order by address offset.

The MPU registers can only be accessed from privileged mode.

Register 80: MPU Type (MPUTYPE), offset 0xD90


Note: This register can only be accessed from privileged mode.

The **MPUTYPE** register indicates whether the MPU is present, and if so, how many regions it supports.

MPU Type (MPUTYPE)

Base 0xE000.E000 Offset 0xD90

Type RO, reset 0x0000.0800



7:1 reserved RO 0x00 Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.

0 SEPARATE RO 0 Separate or Unified MPU

Value Description

0 Indicates the MPU is unified.

Register 81: MPU Control (MPUCTRL), offset 0xD94

Note: This register can only be accessed from privileged mode.

The **MPUCTRL** register enables the MPU, enables the default memory map background region, and enables use of the MPU when in the hard fault, Non-maskable Interrupt (NMI), and **Fault Mask Register (FAULTMASK)** escalated handlers.

When the ENABLE and PRIVDEFEN bits are both set:

- For privileged accesses, the default memory map is as described in "Memory Model" on page 96. Any access by privileged software that does not address an enabled memory region behaves as defined by the default memory map.
- Any access by unprivileged software that does not address an enabled memory region causes a memory management fault.

Execute Never (XN) and Strongly Ordered rules always apply to the System Control Space regardless of the value of the ENABLE bit.


When the ENABLE bit is set, at least one region of the memory map must be enabled for the system to function unless the PRIVDEFEN bit is set. If the PRIVDEFEN bit is set and no regions are enabled, then only privileged software can operate.

When the ENABLE bit is clear, the system uses the default memory map, which has the same memory attributes as if the MPU is not implemented (see Table 2-5 on page 100 for more information). The default memory map applies to accesses from both privileged and unprivileged software.

When the MPU is enabled, accesses to the System Control Space and vector table are always permitted. Other areas are accessible based on regions and whether PRIVDEFEN is set.


Unless HFNMIENA is set, the MPU is not enabled when the processor is executing the handler for an exception with priority -1 or -2. These priorities are only possible when handling a hard fault or NMI exception or when **FAULTMASK** is enabled. Setting the HFNMIENA bit enables the MPU when operating with these two priorities.

MPU Control (MPUCTRL)



Bit/Field

Name



Reset

Type

31:3 reserved RO 0x0000.000 Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.

Description

Bit/Field	Name	Туре	Reset	Description
2	PRIVDEFEN	R/W	0	MPU Default Region
				This bit enables privileged software access to the default memory map.
				Value Description
				0 If the MPU is enabled, this bit disables use of the default memory map. Any memory access to a location not covered by any enabled region causes a fault.
				1 If the MPU is enabled, this bit enables use of the default memory map as a background region for privileged software accesses.
				When this bit is set, the background region acts as if it is region number -1. Any region that is defined and enabled has priority over this default map.
				If the MPU is disabled, the processor ignores this bit.
1	HFNMIENA	R/W	0	MPU Enabled During Faults
				This bit controls the operation of the MPU during hard fault, NMI, and FAULTMASK handlers.
				Value Description
				The MPU is disabled during hard fault, NMI, and FAULTMASK handlers, regardless of the value of the ENABLE bit.
				1 The MPU is enabled during hard fault, NMI, and FAULTMASK handlers.
				When the MPU is disabled and this bit is set, the resulting behavior is unpredictable.
0	ENABLE	R/W	0	MPU Enable
				Value Description
				0 The MPU is disabled.
				1 The MPU is enabled.
				When the MPU is disabled and the HFNMIENA bit is set, the resulting behavior is unpredictable.

Register 82: MPU Region Number (MPUNUMBER), offset 0xD98


Note: This register can only be accessed from privileged mode.

The MPUNUMBER register selects which memory region is referenced by the MPU Region Base Address (MPUBASE) and MPU Region Attribute and Size (MPUATTR) registers. Normally, the required region number should be written to this register before accessing the MPUBASE or the MPUATTR register. However, the region number can be changed by writing to the MPUBASE register with the VALID bit set (see page 194). This write updates the value of the REGION field.

MPU Region Number (MPUNUMBER)

Base 0xE000.E000 Offset 0xD98

Type R/W, reset 0x0000.0000



Bit/Field	Name	Type	Reset	Description
31:3	reserved	RO	0x0000.000	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
2:0	NUMBER	R/W	0x0	MPU Region to Access

This field indicates the MPU region referenced by the **MPUBASE** and **MPUATTR** registers. The MPU supports eight memory regions.

Register 83: MPU Region Base Address (MPUBASE), offset 0xD9C

Register 84: MPU Region Base Address Alias 1 (MPUBASE1), offset 0xDA4

Register 85: MPU Region Base Address Alias 2 (MPUBASE2), offset 0xDAC

Register 86: MPU Region Base Address Alias 3 (MPUBASE3), offset 0xDB4

Note: This register can only be accessed from privileged mode.

The MPUBASE register defines the base address of the MPU region selected by the MPU Region Number (MPUNUMBER) register and can update the value of the MPUNUMBER register. To change the current region number and update the MPUNUMBER register, write the MPUBASE register with the VALID bit set.

The ADDR field is bits 31:*N* of the **MPUBASE** register. Bits (*N*-1):5 are reserved. The region size, as specified by the SIZE field in the **MPU Region Attribute and Size (MPUATTR)** register, defines the value of *N* where:

 $N = Log_2$ (Region size in bytes)


If the region size is configured to 4 GB in the **MPUATTR** register, there is no valid ADDR field. In this case, the region occupies the complete memory map, and the base address is 0x0000.0000.

The base address is aligned to the size of the region. For example, a 64-KB region must be aligned on a multiple of 64 KB, for example, at 0x0001.0000 or 0x0002.0000.

MPU Region Base Address (MPUBASE)

Base 0xE000.E000 Offset 0xD9C

Type R/W, reset 0x0000.0000



Bit/Field Name Type Reset Description

31:5 ADDR R/W 0x0000.000 Base Address Mask

Bits 31:N in this field contain the region base address. The value of N depends on the region size, as shown above. The remaining bits (N-1):5 are reserved.

Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.

Bit/Field	Name	Туре	Reset	Description	
4	VALID	WO	0	Region Number Valid	
				Value Description	
				The MPUNUMBER register is not changed and the processor updates the base address for the region specified in the MPUNUMBER register and ignores the value of the REGION field.	
				The MPUNUMBER register is updated with the value of the REGION field and the base address is updated for the region specified in the REGION field.	
				This bit is always read as 0.	
3	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.	
2:0	REGION	R/W	0x0	Region Number On a write, contains the value to be written to the MPUNUMBER regis On a read, returns the current region number in the MPUNUMBER register.	

Register 87: MPU Region Attribute and Size (MPUATTR), offset 0xDA0

Register 88: MPU Region Attribute and Size Alias 1 (MPUATTR1), offset 0xDA8

Register 89: MPU Region Attribute and Size Alias 2 (MPUATTR2), offset 0xDB0

Register 90: MPU Region Attribute and Size Alias 3 (MPUATTR3), offset 0xDB8

Note: This register can only be accessed from privileged mode.

The **MPUATTR** register defines the region size and memory attributes of the MPU region specified by the **MPU Region Number (MPUNUMBER)** register and enables that region and any subregions.

The **MPUATTR** register is accessible using word or halfword accesses with the most-significant halfword holding the region attributes and the least-significant halfword holds the region size and the region and subregion enable bits.

The MPU access permission attribute bits, XN, AP, TEX, S, C, and B, control access to the corresponding memory region. If an access is made to an area of memory without the required permissions, then the MPU generates a permission fault.

The SIZE field defines the size of the MPU memory region specified by the **MPUNUMBER** register as follows:

(Region size in bytes) = $2^{(SIZE+1)}$

The smallest permitted region size is 32 bytes, corresponding to a SIZE value of 4. Table 3-10 on page 196 gives example SIZE values with the corresponding region size and value of N in the MPU Region Base Address (MPUBASE) register.

Table 3-10. Example SIZE Field Values


SIZE Encoding	Region Size	Value of N ^a	Note
00100b (0x4)	32 B	5	Minimum permitted size
01001b (0x9)	1 KB	10	-
10011b (0x13)	1 MB	20	-
11101b (0x1D)	1 GB	30	-
11111b (0x1F)	4 GB	No valid ADDR field in MPUBASE ; the region occupies the complete memory map.	Maximum possible size

a. Refers to the N parameter in the MPUBASE register (see page 194).

MPU Region Attribute and Size (MPUATTR)

Base 0xE000.E000 Offset 0xDA0

Type R/W, reset 0x0000.0000



Bit/Field	Name	Туре	Reset	Description
31:29	reserved	RO	0x00	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
28	XN	R/W	0	Instruction Access Disable
				Value Description
				0 Instruction fetches are enabled.
				1 Instruction fetches are disabled.
27	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
26:24	AP	R/W	0	Access Privilege
				For information on using this bit field, see Table 3-5 on page 133.
23:22	reserved	RO	0x0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
21:19	TEX	R/W	0x0	Type Extension Mask
				For information on using this bit field, see Table 3-3 on page 132.
18	S	R/W	0	Shareable For information on using this bit, see Table 3-3 on page 132.
17	С	R/W	0	Cacheable For information on using this bit, see Table 3-3 on page 132.
16	В	R/W	0	Bufferable
10	5		ŭ	For information on using this bit, see Table 3-3 on page 132.
15:8	SRD	R/W	0x00	Subregion Disable Bits
				Value Description
				The corresponding subregion is enabled.
				1 The corresponding subregion is disabled.
				Region sizes of 128 bytes and less do not support subregions. When writing the attributes for such a region, configure the SRD field as 0x00. See the section called "Subregions" on page 132 for more information.
7:6	reserved	RO	0x0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
5:1	SIZE	R/W	0x0	Region Size Mask
				The SIZE field defines the size of the MPU memory region specified by the MPUNUMBER register. Refer to Table 3-10 on page 196 for more information.

Bit/Field	Name	Туре	Reset	Description
0	ENABLE	R/W	0	Region Enable
				Value Description
				0 The region is disabled.
				1 The region is enabled.

3.7 Floating-Point Unit (FPU) Register Descriptions

This section lists and describes the Floating-Point Unit (FPU) registers, in numerical order by address offset.

Register 91: Coprocessor Access Control (CPAC), offset 0xD88

The **CPAC** register specifies the access privileges for coprocessors.

Coprocessor Access Control (CPAC)

Base 0xE000.E000 Offset 0xD88

	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16
				rese	rved				CI	P11	CI	P10		rese	rved	
Type Reset	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	R/W 0	R/W 0	R/W 0	R/W 0	RO 0	RO 0	RO 0	RO 0
_	15	14	13	12	11	10	9	8	7	6	5	4	3	2	1	0
	1						' '	rese	rved	1	•	•		ı		ı
Type eset	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0
В	it/Field		Nam	ne	Ту	ре	Reset	Des	cription							
	31:24		reserv	/ed	R	0	0x00	com	patibility	with fut	ure prod	he value ucts, the dify-write	value of	a reserv		
	23:22		CP1	1	R/	W	0x00	CP1	1 Copro	cessor A	Access F	rivilege				
								Valu	ue Desc	cription						
								0x0	Acce	ess Deni	ed					
									Any	attempte	ed acces	s genera	tes a NO	OCP Usa	ge Fault	
								0x1	Privi	leged Ac	cess On	ıly				
									An u	nprivileg	ed acce	ss gener	ates a N	OCP fau	lt.	
								0x2	Rese	erved						
									The	result of	any acc	ess is un	predicta	ble.		
								0x3	Full	Access						
	21:20		CP1	0	R/	W	0x00	CP1	0 Copro	ocessor A	Access F	Privilege				
								Valu	ue Desc	cription						
								0x0		ess Deni	ed					
												s genera	tes a NO	OCP Usa	ge Fault	_
								0x1	Privi	leged Ac	cess On	ıly			•	
										-		ss gener	ates a N	OCP fau	lt.	
								0x2	Rese	erved		•				
									The	result of	any acc	ess is un	predicta	ble.		
								0x3	Full	Access						
	19:0		reserv	/ed	R	0	0x00	com	patibility	with fut	ure prod	he value ucts, the dify-write	value of	a reserv	•	

Register 92: Floating-Point Context Control (FPCC), offset 0xF34

The FPCC register sets or returns FPU control data.

Floating-Point Context Control (FPCC)

BFRDY

MMRDY

5

R/W

R/W

0

0

Base 0xE000.E000

31

Offset 0xF34
Type R/W, reset 0xC000.0000

	ASPEN	LSPEN			1		1	1	rese	rved	1			· · ·		•
Type L	R/W	R/W	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO
Reset	1	1	0	0	0	0	0	0	0	0	0	0	0	0	0	0
	15	14	13	12	11	10	9	8	7	6	5	4	3	2	1	0
		'		reserved	'		'	MONRDY	reserved	BFRDY	MMRDY	HFRDY	THREAD	reserved	USER	LSPACT
Type Reset	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	R/W 0	RO 0	R/W 0	R/W 0	R/W 0	R/W 0	RO 0	R/W 0	R/W 0
В	sit/Field		Nan	ne	Туј	ре	Reset	Des	cription							
	31		ASPI	EN	R/	W	1	Auto	matic S	tate Pres	servation	Enable				
								on e	execution	of a floa	ating-poi	nt instru	ction. Th	n the CO is results or floatin	in auto	matic
								lmį	oortan	bit in regist	the Floa	ting-Po	int Cont	n be ena ext Cont n the Aux	rol (FP	CC)
	30		LSPI	ΕN	R/	W	1	Lazy	v State F	reserva	tion Enat	ole				
									en set, ei				ite prese	rvation fo	or floatin	g-point
	29:9		reser	ved	R	0	0x00	com	patibility	with fut	ure produ	ucts, the		erved bit a reserv on.		
	8		MONE	RDY	R/	W	0	Mor	itor Rea	dv						
								Whe	en set, D	ebugMo				ity permi me was a		
	7		reser	ved	R	0	0	com	patibility	with fut	ure produ	ucts, the		erved bit a reserv on.		

Bus Fault Ready

frame was allocated.

Memory Management Fault Ready

allocated.

When set, BusFault is enabled and priority permitted setting the BusFault handler to the pending state when the floating-point stack frame was

When set, MemManage is enabled and priority permitted setting the MemManage handler to the pending state when the floating-point stack


Bit/Field	Name	Туре	Reset	Description
4	HFRDY	R/W	0	Hard Fault Ready When set, priority permitted setting the HardFault handler to the pending state when the floating-point stack frame was allocated.
3	THREAD	R/W	0	Thread Mode When set, mode was Thread Mode when the floating-point stack frame was allocated.
2	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
1	USER	R/W	0	User Privilege Level When set, privilege level was user when the floating-point stack frame was allocated.
0	LSPACT	R/W	0	Lazy State Preservation Active When set, Lazy State preservation is active. Floating-point stack frame has been allocated but saving state to it has been deferred.

Register 93: Floating-Point Context Address (FPCA), offset 0xF38

The **FPCA** register holds the location of the unpopulated floating-point register space allocated on an exception stack frame.

Floating-Point Context Address (FPCA)

Base 0xE000.E000 Offset 0xF38 Type R/W, reset -



Bit/Field	Name	Туре	Reset	Description
31:3	ADDRESS	R/W	-	Address The location of the unpopulated floating-point register space allocated on an exception stack frame.
2:0	reserved	RO	0x00	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.

Register 94: Floating-Point Default Status Control (FPDSC), offset 0xF3C

The FPDSC register holds the default values for the Floating-Point Status Control (FPSC) register.

Floating-Point Default Status Control (FPDSC)

Base 0xE000.E000 Offset 0xF3C

21:0

reserved

RO

Type R/W, reset 0x0000.0000

_	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16
			reserved			AHP	DN	FZ	RM	ODE		•	rese	rved		
Туре	RO	RO	RO	RO	RO	R/W	R/W	R/W	R/W	R/W	RO	RO	RO	RO	RO	RO
Reset	0	0	0	0	0	-	-	-	-	-	0	0	0	0	0	0
	15	14	13	12	11	10	9	8	7	6	5	4	3	2	1	0
			'				•	rese	erved	'	'	'		'		
Туре	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO
Reset	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0
Е	Bit/Field		Nam	ne	Ту	ре	Reset	Des	cription							
	31:27		reser	ved	R	0	0x00	com	patibility	with futu	ure prod	he value ucts, the dify-write	value of	a reserv		
	26		AHI	P	R/	W	-		P Bit Def		fault valu	ue for the	AHP bit	in the FF	PSC reg	ster.
	25		DN	ı	R/	۱۸/	_	DN	Bit Defa	ult						
	25		יום	•	IV	vv	_									
								Ihis	bit hold	s the def	ault valu	ue for the	DN bit ii	n the FP	SC regis	ter.
	24		FZ		R/	W	_	FZ E	Bit Defau	ılt						
								This	bit hold	s the def	fault valu	ue for the	FZ bit in	n the FP	SC regis	ter.
	23:22		RMO	DE	R/	W	-	RM	ODE Bit	Default						
									s bit hold ster.	s the def	fault valu	ue for the	RMODE	bit field i	n the FP	SC

Value Description

0x0 Round to Nearest (RN) mode

0x1 Round towards Plus Infinity (RP) mode

0x2 Round towards Minus Infinity (RM) mode

0x3 Round towards Zero (RZ) mode

0x00 Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be

preserved across a read-modify-write operation.

4 JTAG Interface

The Joint Test Action Group (JTAG) port is an IEEE standard that defines a Test Access Port and Boundary Scan Architecture for digital integrated circuits and provides a standardized serial interface for controlling the associated test logic. The TAP, Instruction Register (IR), and Data Registers (DR) can be used to test the interconnections of assembled printed circuit boards and obtain manufacturing information on the components. The JTAG Port also provides a means of accessing and controlling design-for-test features such as I/O pin observation and control, scan testing, and debugging.

The JTAG port is comprised of four pins: TCK, TMS, TDI, and TDO. Data is transmitted serially into the controller on TDI and out of the controller on TDO. The interpretation of this data is dependent on the current state of the TAP controller. For detailed information on the operation of the JTAG port and TAP controller, please refer to the *IEEE Standard 1149.1-Test Access Port and Boundary-Scan Architecture*.

The Stellaris[®] JTAG controller works with the ARM JTAG controller built into the Cortex-M4F core by multiplexing the TDO outputs from both JTAG controllers. ARM JTAG instructions select the ARM TDO output while Stellaris JTAG instructions select the Stellaris TDO output. The multiplexer is controlled by the Stellaris JTAG controller, which has comprehensive programming for the ARM, Stellaris, and unimplemented JTAG instructions.


The Stellaris JTAG module has the following features:

- IEEE 1149.1-1990 compatible Test Access Port (TAP) controller
- Four-bit Instruction Register (IR) chain for storing JTAG instructions
- IEEE standard instructions: BYPASS, IDCODE, SAMPLE/PRELOAD, EXTEST and INTEST
- ARM additional instructions: APACC, DPACC and ABORT
- Integrated ARM Serial Wire Debug (SWD)
 - Serial Wire JTAG Debug Port (SWJ-DP)
 - Flash Patch and Breakpoint (FPB) unit for implementing breakpoints
 - Data Watchpoint and Trace (DWT) unit for implementing watchpoints, trigger resources, and system profiling
 - Instrumentation Trace Macrocell (ITM) for support of printf style debugging
 - Embedded Trace Macrocell (ETM) for instruction trace capture
 - Trace Port Interface Unit (TPIU) for bridging to a Trace Port Analyzer

See the ARM® Debug Interface V5 Architecture Specification for more information on the ARM JTAG controller.

4.1 Block Diagram

Figure 4-1. JTAG Module Block Diagram



4.2 Signal Description

The following table lists the external signals of the JTAG/SWD controller and describes the function of each. The JTAG/SWD controller signals are alternate functions for some GPIO signals, however note that the reset state of the pins is for the JTAG/SWD function. The JTAG/SWD controller signals are under commit protection and require a special process to be configured as GPIOs, see "Commit Control" on page 654. The column in the table below titled "Pin Mux/Pin Assignment" lists the GPIO pin placement for the JTAG/SWD controller signals. The AFSEL bit in the **GPIO Alternate Function Select (GPIOAFSEL)** register (page 670) is set to choose the JTAG/SWD function. The number in parentheses is the encoding that must be programmed into the PMCn field in the **GPIO Port Control (GPIOPCTL)** register (page 688) to assign the JTAG/SWD controller signals to the specified GPIO port pin. For more information on configuring GPIOs, see "General-Purpose Input/Outputs (GPIOs)" on page 646.

Table 4-1. JTAG_SWD_SWO Signals (100LQFP)

Pin Name	Pin Number	Pin Mux / Pin Assignment	Pin Type	Buffer Type ^a	Description
SWCLK	85	PC0 (1)	1	TTL	JTAG/SWD CLK.
SWDIO	84	PC1 (1)	I/O	TTL	JTAG TMS and SWDIO.
SWO	82	PC3 (1)	0	TTL	JTAG TDO and SWO.
TCK	85	PC0 (1)	1	TTL	JTAG/SWD CLK.
TDI	83	PC2 (1)	1	TTL	JTAG TDI.
TDO	82	PC3 (1)	0	TTL	JTAG TDO and SWO.

Table 4-1. JTAG_SWD_SWO Signals (100LQFP) (continued)

Pin Name	Pin Number	Pin Mux / Pin Assignment	Pin Type	Buffer Type ^a	Description
TMS	84	PC1 (1)	I	TTL	JTAG TMS and SWDIO.

a. The TTL designation indicates the pin has TTL-compatible voltage levels.

4.3 Functional Description

A high-level conceptual drawing of the JTAG module is shown in Figure 4-1 on page 205. The JTAG module is composed of the Test Access Port (TAP) controller and serial shift chains with parallel update registers. The TAP controller is a simple state machine controlled by the TCK and TMS inputs. The current state of the TAP controller depends on the sequence of values captured on TMS at the rising edge of TCK. The TAP controller determines when the serial shift chains capture new data, shift data from TDI towards TDO, and update the parallel load registers. The current state of the TAP controller also determines whether the Instruction Register (IR) chain or one of the Data Register (DR) chains is being accessed.

The serial shift chains with parallel load registers are comprised of a single Instruction Register (IR) chain and multiple Data Register (DR) chains. The current instruction loaded in the parallel load register determines which DR chain is captured, shifted, or updated during the sequencing of the TAP controller.

Some instructions, like EXTEST and INTEST, operate on data currently in a DR chain and do not capture, shift, or update any of the chains. Instructions that are not implemented decode to the BYPASS instruction to ensure that the serial path between TDI and TDO is always connected (see Table 4-3 on page 212 for a list of implemented instructions).

See "JTAG and Boundary Scan" on page 1381 for JTAG timing diagrams.

Note: Of all the possible reset sources, only Power-On reset (POR) and the assertion of the RST input have any effect on the JTAG module. The pin configurations are reset by both the RST input and POR, whereas the internal JTAG logic is only reset with POR. See "Reset Sources" on page 217 for more information on reset.

4.3.1 JTAG Interface Pins

The JTAG interface consists of four standard pins: TCK, TMS, TDI, and TDO. These pins and their associated state after a power-on reset or reset caused by the RST input are given in Table 4-2. Detailed information on each pin follows.

Note: The following pins are configured as JTAG port pins out of reset. Refer to "General-Purpose Input/Outputs (GPIOs)" on page 646 for information on how to reprogram the configuration of these pins.

Table 4-2. JTAG Port Pins State after Power-On Reset or RST assertion

Pin Name	Data Direction	Internal Pull-Up	Internal Pull-Down	Drive Strength	Drive Value	
TCK	Input	Enabled	Disabled	N/A	N/A	
TMS	Input	Enabled	Disabled	N/A	N/A	
TDI	Input	Enabled	Disabled	N/A	N/A	
TDO	Output	Enabled	Disabled	2-mA driver	High-Z	

4.3.1.1 Test Clock Input (TCK)

The TCK pin is the clock for the JTAG module. This clock is provided so the test logic can operate independently of any other system clocks and to ensure that multiple JTAG TAP controllers that are daisy-chained together can synchronously communicate serial test data between components. During normal operation, TCK is driven by a free-running clock with a nominal 50% duty cycle. When necessary, TCK can be stopped at 0 or 1 for extended periods of time. While TCK is stopped at 0 or 1, the state of the TAP controller does not change and data in the JTAG Instruction and Data Registers is not lost.

By default, the internal pull-up resistor on the ${\tt TCK}$ pin is enabled after reset, assuring that no clocking occurs if the pin is not driven from an external source. The internal pull-up and pull-down resistors can be turned off to save internal power as long as the ${\tt TCK}$ pin is constantly being driven by an external source (see page 676 and page 678).

4.3.1.2 Test Mode Select (TMS)

The TMS pin selects the next state of the JTAG TAP controller. TMS is sampled on the rising edge of TCK. Depending on the current TAP state and the sampled value of TMS, the next state may be entered. Because the TMS pin is sampled on the rising edge of TCK, the *IEEE Standard 1149.1* expects the value on TMS to change on the falling edge of TCK.

Holding TMS high for five consecutive TCK cycles drives the TAP controller state machine to the Test-Logic-Reset state. When the TAP controller enters the Test-Logic-Reset state, the JTAG module and associated registers are reset to their default values. This procedure should be performed to initialize the JTAG controller. The JTAG Test Access Port state machine can be seen in its entirety in Figure 4-2 on page 208.

By default, the internal pull-up resistor on the TMS pin is enabled after reset. Changes to the pull-up resistor settings on GPIO Port C should ensure that the internal pull-up resistor remains enabled on PC1/TMS; otherwise JTAG communication could be lost (see page 676).

4.3.1.3 Test Data Input (TDI)

The TDI pin provides a stream of serial information to the IR chain and the DR chains. TDI is sampled on the rising edge of TCK and, depending on the current TAP state and the current instruction, may present this data to the proper shift register chain. Because the TDI pin is sampled on the rising edge of TCK, the *IEEE Standard 1149.1* expects the value on TDI to change on the falling edge of TCK.

By default, the internal pull-up resistor on the TDI pin is enabled after reset. Changes to the pull-up resistor settings on GPIO Port C should ensure that the internal pull-up resistor remains enabled on PC2/TDI; otherwise JTAG communication could be lost (see page 676).

4.3.1.4 Test Data Output (TDO)

The TDO pin provides an output stream of serial information from the IR chain or the DR chains. The value of TDO depends on the current TAP state, the current instruction, and the data in the chain being accessed. In order to save power when the JTAG port is not being used, the TDO pin is placed in an inactive drive state when not actively shifting out data. Because TDO can be connected to the TDI of another controller in a daisy-chain configuration, the *IEEE Standard 1149.1* expects the value on TDO to change on the falling edge of TCK.

By default, the internal pull-up resistor on the TDO pin is enabled after reset, assuring that the pin remains at a constant logic level when the JTAG port is not being used. The internal pull-up and

pull-down resistors can be turned off to save internal power if a High-Z output value is acceptable during certain TAP controller states (see page 676 and page 678).

4.3.2 JTAG TAP Controller

The JTAG TAP controller state machine is shown in Figure 4-2. The TAP controller state machine is reset to the Test-Logic-Reset state on the assertion of a Power-On-Reset (POR). In order to reset the JTAG module after the microcontroller has been powered on, the TMS input must be held HIGH for five TCK clock cycles, resetting the TAP controller and all associated JTAG chains. Asserting the correct sequence on the TMS pin allows the JTAG module to shift in new instructions, shift in data, or idle during extended testing sequences. For detailed information on the function of the TAP controller and the operations that occur in each state, please refer to *IEEE Standard 1149.1*.

Test Logic Reset 0 Select DR Scar Select IR Scan Run Test Idle 0 0 Capture DR Capture IR 0 0 Shift DR Shift IR Exit 1 DR Exit 1 IR 0 0 Pause DR Pause IR Exit 2 DR Exit 2 IR Update DR Update IR 1 0 1 0

Figure 4-2. Test Access Port State Machine

4.3.3 Shift Registers

The Shift Registers consist of a serial shift register chain and a parallel load register. The serial shift register chain samples specific information during the TAP controller's CAPTURE states and allows this information to be shifted out on TDO during the TAP controller's SHIFT states. While the sampled data is being shifted out of the chain on TDO, new data is being shifted into the serial shift register on TDI. This new data is stored in the parallel load register during the TAP controller's UPDATE states. Each of the shift registers is discussed in detail in "Register Descriptions" on page 211.

4.3.4 Operational Considerations

Certain operational parameters must be considered when using the JTAG module. Because the JTAG pins can be programmed to be GPIOs, board configuration and reset conditions on these pins must be considered. In addition, because the JTAG module has integrated ARM Serial Wire Debug, the method for switching between these two operational modes is described below.

4.3.4.1 GPIO Functionality

When the microcontroller is reset with either a POR or $\overline{\mathtt{RST}}$, the JTAG/SWD port pins default to their JTAG/SWD configurations. The default configuration includes enabling digital functionality (DEN[3:0] set in the **Port C GPIO Digital Enable (GPIODEN)** register), enabling the pull-up resistors (PUE[3:0] set in the **Port C GPIO Pull-Up Select (GPIOPUR)** register), disabling the pull-down resistors (PDE[3:0] cleared in the **Port C GPIO Pull-Down Select (GPIOPDR)** register) and enabling the alternate hardware function (AFSEL[3:0] set in the **Port C GPIO Alternate Function Select (GPIOAFSEL)** register) on the JTAG/SWD pins. See page 670, page 676, page 678, and page 681.

It is possible for software to configure these pins as GPIOs after reset by clearing AFSEL[3:0] in the **Port C GPIOAFSEL** register. If the user does not require the JTAG/SWD port for debugging or board-level testing, this provides four more GPIOs for use in the design.

Caution – It is possible to create a software sequence that prevents the debugger from connecting to the Stellaris microcontroller. If the program code loaded into flash immediately changes the JTAG pins to their GPIO functionality, the debugger may not have enough time to connect and halt the controller before the JTAG pin functionality switches. As a result, the debugger may be locked out of the part. This issue can be avoided with a software routine that restores JTAG functionality based on an external or software trigger. In the case that the software routine is not implemented and the device is locked out of the part, this issue can be solved by using the Stellaris Flash Programmer "Unlock" feature. Please refer to LMFLASHPROGRAMMER on the TI web for more information.

The GPIO commit control registers provide a layer of protection against accidental programming of critical hardware peripherals. Protection is provided for the GPIO pins that can be used as the four JTAG/SWD pins (PC[3:0]) and the NMI pin (PD7 and PF0). Writes to protected bits of the GPIO Alternate Function Select (GPIOAFSEL) register (see page 670), GPIO Pull Up Select (GPIOPUR) register (see page 676), GPIO Pull-Down Select (GPIOPDR) register (see page 678), and GPIO Digital Enable (GPIODEN) register (see page 681) are not committed to storage unless the GPIO Lock (GPIOLOCK) register (see page 683) has been unlocked and the appropriate bits of the GPIO Commit (GPIOCR) register (see page 684) have been set.

4.3.4.2 Communication with JTAG/SWD

Because the debug clock and the system clock can be running at different frequencies, care must be taken to maintain reliable communication with the JTAG/SWD interface. In the Capture-DR state, the result of the previous transaction, if any, is returned, together with a 3-bit ACK response. Software should check the ACK response to see if the previous operation has completed before initiating a new transaction. Alternatively, if the system clock is at least 8 times faster than the debug clock (TCK or SWCLK), the previous operation has enough time to complete and the ACK bits do not have to be checked.

4.3.4.3 Recovering a "Locked" Microcontroller

Note: Performing the sequence below restores the non-volatile registers discussed in "Non-Volatile Register Programming" on page 530 to their factory default values. The mass erase of the Flash memory caused by the sequence below occurs prior to the non-volatile registers being restored.

In addition, the EEPROM is erased and its wear-leveling counters are returned to factory default values when performing the sequence below.

If software configures any of the JTAG/SWD pins as GPIO and loses the ability to communicate with the debugger, there is a debug port unlock sequence that can be used to recover the microcontroller. Performing a total of ten JTAG-to-SWD and SWD-to-JTAG switch sequences while holding the microcontroller in reset mass erases the Flash memory. The debug port unlock sequence is:

- 1. Assert and hold the \overline{RST} signal.
- 2. Apply power to the device.
- Perform steps 1 and 2 of the JTAG-to-SWD switch sequence on the section called "JTAG-to-SWD Switching" on page 211.
- **4.** Perform steps 1 and 2 of the SWD-to-JTAG switch sequence on the section called "SWD-to-JTAG Switching" on page 211.
- 5. Perform steps 1 and 2 of the JTAG-to-SWD switch sequence.
- 6. Perform steps 1 and 2 of the SWD-to-JTAG switch sequence.
- 7. Perform steps 1 and 2 of the JTAG-to-SWD switch sequence.
- **8.** Perform steps 1 and 2 of the SWD-to-JTAG switch sequence.
- **9.** Perform steps 1 and 2 of the JTAG-to-SWD switch sequence.
- **10.** Perform steps 1 and 2 of the SWD-to-JTAG switch sequence.
- **11.** Perform steps 1 and 2 of the JTAG-to-SWD switch sequence.
- **12.** Perform steps 1 and 2 of the SWD-to-JTAG switch sequence.
- **13.** Release the \overline{RST} signal.
- 14. Wait 400 ms.
- **15.** Power-cycle the microcontroller.

4.3.4.4 ARM Serial Wire Debug (SWD)

In order to seamlessly integrate the ARM Serial Wire Debug (SWD) functionality, a serial-wire debugger must be able to connect to the Cortex-M4F core without having to perform, or have any knowledge of, JTAG cycles. This integration is accomplished with a SWD preamble that is issued before the SWD session begins.

The switching preamble used to enable the SWD interface of the SWJ-DP module starts with the TAP controller in the Test-Logic-Reset state. From here, the preamble sequences the TAP controller through the following states: Run Test Idle, Select DR, Select IR, Test Logic Reset, Test Logic Reset, Run Test Idle, Run Test Idle, Select DR, Select IR, Test Logic Reset, Test Logic Reset, Run Test Idle, Select DR, Select IR, and Test Logic Reset states.

Stepping through this sequence of the TAP state machine enables the SWD interface and disables the JTAG interface. For more information on this operation and the SWD interface, see the *ARM® Debug Interface V5 Architecture Specification*.

Because this sequence is a valid series of JTAG operations that could be issued, the ARM JTAG TAP controller is not fully compliant to the *IEEE Standard 1149.1*. This instance is the only one where the ARM JTAG TAP controller does not meet full compliance with the specification. Due to the low probability of this sequence occurring during normal operation of the TAP controller, it should not affect normal performance of the JTAG interface.

JTAG-to-SWD Switching

To switch the operating mode of the Debug Access Port (DAP) from JTAG to SWD mode, the external debug hardware must send the switching preamble to the microcontroller. The 16-bit TMS command for switching to SWD mode is defined as b1110.0111.1001.1110, transmitted LSB first. This command can also be represented as 0xE79E when transmitted LSB first. The complete switch sequence should consist of the following transactions on the TCK/SWCLK and TMS/SWDIO signals:

- 1. Send at least 50 TCK/SWCLK cycles with TMS/SWDIO High to ensure that both JTAG and SWD are in their reset/idle states.
- 2. Send the 16-bit JTAG-to-SWD switch command, 0xE79E, on TMS.
- 3. Send at least 50 TCK/SWCLK cycles with TMS/SWDIO High to ensure that if SWJ-DP was already in SWD mode, the SWD goes into the line reset state before sending the switch sequence.

SWD-to-JTAG Switching

To switch the operating mode of the Debug Access Port (DAP) from SWD to JTAG mode, the external debug hardware must send a switch command to the microcontroller. The 16-bit TMS command for switching to JTAG mode is defined as b1110.0111.0011.1100, transmitted LSB first. This command can also be represented as 0xE73C when transmitted LSB first. The complete switch sequence should consist of the following transactions on the TCK/SWCLK and TMS/SWDIO signals:

- 1. Send at least 50 TCK/SWCLK cycles with TMS/SWDIO High to ensure that both JTAG and SWD are in their reset/idle states.
- 2. Send the 16-bit SWD-to-JTAG switch command, 0xE73C, on TMS.
- 3. Send at least 50 TCK/SWCLK cycles with TMS/SWDIO High to ensure that if SWJ-DP was already in JTAG mode, the JTAG goes into the Test Logic Reset state before sending the switch sequence.

4.4 Initialization and Configuration

After a Power-On-Reset or an external reset (\overline{RST}), the JTAG pins are automatically configured for JTAG communication. No user-defined initialization or configuration is needed. However, if the user application changes these pins to their GPIO function, they must be configured back to their JTAG functionality before JTAG communication can be restored. To return the pins to their JTAG functions, enable the four JTAG pins (PC[3:0]) for their alternate function using the **GPIOAFSEL** register. In addition to enabling the alternate functions, any other changes to the GPIO pad configurations on the four JTAG pins (PC[3:0]) should be returned to their default settings.

4.5 Register Descriptions

The registers in the JTAG TAP Controller or Shift Register chains are not memory mapped and are not accessible through the on-chip Advanced Peripheral Bus (APB). Instead, the registers within the JTAG controller are all accessed serially through the TAP Controller. These registers include the Instruction Register and the six Data Registers.

4.5.1 Instruction Register (IR)

The JTAG TAP Instruction Register (IR) is a four-bit serial scan chain connected between the JTAG TDI and TDO pins with a parallel load register. When the TAP Controller is placed in the correct states, bits can be shifted into the IR. Once these bits have been shifted into the chain and updated, they are interpreted as the current instruction. The decode of the IR bits is shown in Table 4-3. A detailed explanation of each instruction, along with its associated Data Register, follows.

Table 4-3. JTAG Instruction Register Comma	nds
--	-----

IR[3:0]	Instruction	Description
0x0	EXTEST	Drives the values preloaded into the Boundary Scan Chain by the SAMPLE/PRELOAD instruction onto the pads.
0x1	INTEST	Drives the values preloaded into the Boundary Scan Chain by the SAMPLE/PRELOAD instruction into the controller.
0x2	SAMPLE / PRELOAD	Captures the current I/O values and shifts the sampled values out of the Boundary Scan Chain while new preload data is shifted in.
0x8	ABORT	Shifts data into the ARM Debug Port Abort Register.
0xA	DPACC	Shifts data into and out of the ARM DP Access Register.
0xB	APACC	Shifts data into and out of the ARM AC Access Register.
0xE	IDCODE	Loads manufacturing information defined by the <i>IEEE Standard 1149.1</i> into the IDCODE chain and shifts it out.
0xF	BYPASS	Connects TDI to TDO through a single Shift Register chain.
All Others	Reserved	Defaults to the BYPASS instruction to ensure that \mathtt{TDI} is always connected to \mathtt{TDO} .

4.5.1.1 EXTEST Instruction

The EXTEST instruction is not associated with its own Data Register chain. Instead, the EXTEST instruction uses the data that has been preloaded into the Boundary Scan Data Register using the SAMPLE/PRELOAD instruction. When the EXTEST instruction is present in the Instruction Register, the preloaded data in the Boundary Scan Data Register associated with the outputs and output enables are used to drive the GPIO pads rather than the signals coming from the core. With tests that drive known values out of the controller, this instruction can be used to verify connectivity. While the EXTEST instruction is present in the Instruction Register, the Boundary Scan Data Register can be accessed to sample and shift out the current data and load new data into the Boundary Scan Data Register.

4.5.1.2 INTEST Instruction

The INTEST instruction is not associated with its own Data Register chain. Instead, the INTEST instruction uses the data that has been preloaded into the Boundary Scan Data Register using the SAMPLE/PRELOAD instruction. When the INTEST instruction is present in the Instruction Register, the preloaded data in the Boundary Scan Data Register associated with the inputs are used to drive the signals going into the core rather than the signals coming from the GPIO pads. With tests that drive known values into the controller, this instruction can be used for testing. It is important to note that although the RST input pin is on the Boundary Scan Data Register chain, it is only observable. While the INTEST instruction is present in the Instruction Register, the Boundary Scan Data Register can be accessed to sample and shift out the current data and load new data into the Boundary Scan Data Register.

4.5.1.3 SAMPLE/PRELOAD Instruction

The SAMPLE/PRELOAD instruction connects the Boundary Scan Data Register chain between TDI and TDO. This instruction samples the current state of the pad pins for observation and preloads new test data. Each GPIO pad has an associated input, output, and output enable signal. When the TAP controller enters the Capture DR state during this instruction, the input, output, and output-enable signals to each of the GPIO pads are captured. These samples are serially shifted out on TDO while the TAP controller is in the Shift DR state and can be used for observation or comparison in various tests.

While these samples of the inputs, outputs, and output enables are being shifted out of the Boundary Scan Data Register, new data is being shifted into the Boundary Scan Data Register from TDI. Once the new data has been shifted into the Boundary Scan Data Register, the data is saved in the parallel load registers when the TAP controller enters the Update DR state. This update of the parallel load register preloads data into the Boundary Scan Data Register that is associated with each input, output, and output enable. This preloaded data can be used with the EXTEST and INTEST instructions to drive data into or out of the controller. See "Boundary Scan Data Register" on page 214 for more information.

4.5.1.4 ABORT Instruction

The ABORT instruction connects the associated ABORT Data Register chain between TDI and TDO. This instruction provides read and write access to the ABORT Register of the ARM Debug Access Port (DAP). Shifting the proper data into this Data Register clears various error bits or initiates a DAP abort of a previous request. See the "ABORT Data Register" on page 215 for more information.

4.5.1.5 DPACC Instruction

The DPACC instruction connects the associated DPACC Data Register chain between TDI and TDO. This instruction provides read and write access to the DPACC Register of the ARM Debug Access Port (DAP). Shifting the proper data into this register and reading the data output from this register allows read and write access to the ARM debug and status registers. See "DPACC Data Register" on page 215 for more information.

4.5.1.6 APACC Instruction

The APACC instruction connects the associated APACC Data Register chain between <code>TDI</code> and <code>TDO</code>. This instruction provides read and write access to the APACC Register of the ARM Debug Access Port (DAP). Shifting the proper data into this register and reading the data output from this register allows read and write access to internal components and buses through the Debug Port. See "APACC Data Register" on page 215 for more information.

4.5.1.7 IDCODE Instruction

The IDCODE instruction connects the associated IDCODE Data Register chain between TDI and TDO. This instruction provides information on the manufacturer, part number, and version of the ARM core. This information can be used by testing equipment and debuggers to automatically configure input and output data streams. IDCODE is the default instruction loaded into the JTAG Instruction Register when a Power-On-Reset (POR) is asserted, or the Test-Logic-Reset state is entered. See "IDCODE Data Register" on page 214 for more information.

4.5.1.8 BYPASS Instruction

The BYPASS instruction connects the associated BYPASS Data Register chain between \mathtt{TDI} and \mathtt{TDO} . This instruction is used to create a minimum length serial path between the \mathtt{TDI} and \mathtt{TDO} ports. The BYPASS Data Register is a single-bit shift register. This instruction improves test efficiency by

allowing components that are not needed for a specific test to be bypassed in the JTAG scan chain by loading them with the BYPASS instruction. See "BYPASS Data Register" on page 214 for more information.

4.5.2 Data Registers

The JTAG module contains six Data Registers. These serial Data Register chains include: IDCODE, BYPASS, Boundary Scan, APACC, DPACC, and ABORT and are discussed in the following sections.

4.5.2.1 IDCODE Data Register

The format for the 32-bit IDCODE Data Register defined by the *IEEE Standard 1149.1* is shown in Figure 4-3. The standard requires that every JTAG-compliant microcontroller implement either the IDCODE instruction or the BYPASS instruction as the default instruction. The LSB of the IDCODE Data Register is defined to be a 1 to distinguish it from the BYPASS instruction, which has an LSB of 0. This definition allows auto-configuration test tools to determine which instruction is the default instruction.

The major uses of the JTAG port are for manufacturer testing of component assembly and program development and debug. To facilitate the use of auto-configuration debug tools, the IDCODE instruction outputs a value of 0x4BA0.0477. This value allows the debuggers to automatically configure themselves to work correctly with the Cortex-M4F during debug.

Figure 4-3. IDCODE Register Format



4.5.2.2 BYPASS Data Register

The format for the 1-bit BYPASS Data Register defined by the *IEEE Standard 1149.1* is shown in Figure 4-4. The standard requires that every JTAG-compliant microcontroller implement either the BYPASS instruction or the IDCODE instruction as the default instruction. The LSB of the BYPASS Data Register is defined to be a 0 to distinguish it from the IDCODE instruction, which has an LSB of 1. This definition allows auto-configuration test tools to determine which instruction is the default instruction.

Figure 4-4. BYPASS Register Format


4.5.2.3 Boundary Scan Data Register

The format of the Boundary Scan Data Register is shown in Figure 4-5. Each GPIO pin, starting with a GPIO pin next to the JTAG port pins, is included in the Boundary Scan Data Register. Each GPIO pin has three associated digital signals that are included in the chain. These signals are input, output, and output enable, and are arranged in that order as shown in the figure.

When the Boundary Scan Data Register is accessed with the SAMPLE/PRELOAD instruction, the input, output, and output enable from each digital pad are sampled and then shifted out of the chain

to be verified. The sampling of these values occurs on the rising edge of TCK in the Capture DR state of the TAP controller. While the sampled data is being shifted out of the Boundary Scan chain in the Shift DR state of the TAP controller, new data can be preloaded into the chain for use with the EXTEST and INTEST instructions. The EXTEST instruction forces data out of the controller, and the INTEST instruction forces data into the controller.

Figure 4-5. Boundary Scan Register Format



4.5.2.4 APACC Data Register

The format for the 35-bit APACC Data Register defined by ARM is described in the *ARM® Debug Interface V5 Architecture Specification*.

4.5.2.5 DPACC Data Register

The format for the 35-bit DPACC Data Register defined by ARM is described in the *ARM® Debug Interface V5 Architecture Specification*.

4.5.2.6 ABORT Data Register

The format for the 35-bit ABORT Data Register defined by ARM is described in the *ARM® Debug Interface V5 Architecture Specification*.

5 System Control

System control configures the overall operation of the device and provides information about the device. Configurable features include reset control, NMI operation, power control, clock control, and low-power modes.

5.1 Signal Description

The following table lists the external signals of the System Control module and describes the function of each. The NMI signal is the alternate function for two GPIO signals and functions as a GPIO after reset. PD7 and PF0 are under commit protection and require a special process to be configured as any alternate function or to subsequently return to the GPIO function, see "Commit Control" on page 654. The column in the table below titled "Pin Mux/Pin Assignment" lists the GPIO pin placement for the NMI signal. The AFSEL bit in the GPIO Alternate Function Select (GPIOAFSEL) register (page 670) should be set to choose the NMI function. The number in parentheses is the encoding that must be programmed into the PMCn field in the GPIO Port Control (GPIOPCTL) register (page 688) to assign the NMI signal to the specified GPIO port pin. For more information on configuring GPIOs, see "General-Purpose Input/Outputs (GPIOs)" on page 646. The remaining signals (with the word "fixed" in the Pin Mux/Pin Assignment column) have a fixed pin assignment and function.

Table 5-1. System Control & Clocks Signals (100LQFP)

Pin Name	Pin Number	Pin Mux / Pin Assignment	Pin Type	Buffer Type ^a	Description
NMI	40 100	PF0 (8) PD7 (8)	I	TTL	Non-maskable interrupt.
osc0	65	fixed	I	Analog	Main oscillator crystal input or an external clock reference input.
OSC1	66	fixed	0	Analog	Main oscillator crystal output. Leave unconnected when using a single-ended clock source.
RST	63	fixed	ļ	TTL	System reset input.

a. The TTL designation indicates the pin has TTL-compatible voltage levels.

5.2 Functional Description

The System Control module provides the following capabilities:

- Device identification, see "Device Identification" on page 216
- Local control, such as reset (see "Reset Control" on page 217), power (see "Power Control" on page 222) and clock control (see "Clock Control" on page 223)
- System control (Run, Sleep, and Deep-Sleep modes), see "System Control" on page 231

5.2.1 Device Identification

Several read-only registers provide software with information on the microcontroller, such as version, part number, memory sizes, and peripherals present on the device. The **Device Identification 0** (**DID0**) (page 240) and **Device Identification 1** (**DID1**) (page 242) registers provide details about the device's version, package, temperature range, and so on. The Peripheral Present registers starting at System Control offset 0x300, such as the **Watchdog Timer Peripheral Present (PPWD)** register, provide information on how many of each type of module are included on the device. Finally,

information about the capabilities of the on-chip peripherals are provided at offset 0xFC0 in each peripheral's register space in the Peripheral Properties registers, such as the **GPTM Peripheral Properties** (**GPTMPP**) register. Previous generations of Stellaris[®] devices used the **Device Capabilities** (**DC0-DC9**) registers for information about the peripherals and their capabilities. These registers are present on this device for backward software capability, but provide no information about peripherals that were not available on older devices.

5.2.2 Reset Control

This section discusses aspects of hardware functions during reset as well as system software requirements following the reset sequence.

5.2.2.1 Reset Sources

The LM4F232H5QC microcontroller has six sources of reset:

- 1. Power-on reset (POR) (see page 218).
- **2.** External reset input pin (\overline{RST}) assertion (see page 218).
- 3. A brown-out detection that can be caused by any of the following events: (see page 220).
 - V_{DD} under BOR0. The trigger value is the highest V_{DD} voltage level for BOR0.
 - lacktriangledown V_{DD} under BOR1. The trigger value is the highest V_{DD} voltage level for BOR1.
- **4.** Software-initiated reset (with the software reset registers) (see page 221).
- **5.** A watchdog timer reset condition violation (see page 221).
- 6. MOSC failure (see page 222).

Table 5-2 provides a summary of results of the various reset operations.

Table 5-2. Reset Sources

Reset Source	Core Reset?	JTAG Reset?	On-Chip Peripherals Reset?
Power-On Reset	Yes	Yes	Yes
RST	Yes	Pin Config Only	Yes
Brown-Out Reset	Yes	Pin Config Only	Yes
Software System Request Reset using the SYSRESREQ bit in the APINT register.	Yes	Pin Config Only	Yes
Software System Request Reset using the VECTRESET bit in the APINT register.	Yes	Pin Config Only	No
Software Peripheral Reset	No	Pin Config Only	Yes ^a
Watchdog Reset	Yes	Pin Config Only	Yes
MOSC Failure Reset	Yes	Pin Config Only	Yes

a. Programmable on a module-by-module basis using the Software Reset Control Registers.

After a reset, the **Reset Cause (RESC)** register is set with the reset cause. The bits in this register are sticky and maintain their state across multiple reset sequences, except when an internal POR

is the cause, in which case, all the bits in the **RESC** register are cleared except for the POR indicator. A bit in the **RESC** register can be cleared by writing a 0.

At any reset that resets the core, the user has the opportunity to direct the core to execute the ROM Boot Loader or the application in Flash memory by using any GPIO signal as configured in the **Boot Configuration (BOOTCFG)** register.

At reset, the following sequence is performed:

- 1. The **BOOTCFG** register is read. If the EN bit is clear, the ROM Boot Loader is executed.
- 2. In the ROM Boot Loader, the status of the specified GPIO pin is compared with the specified polarity. If the status matches the specified polarity, the ROM is mapped to address 0x0000.0000 and execution continues out of the ROM Boot Loader.
- **3.** If then EN bit is set or the status doesn't match the specified polarity, the data at address 0x0000.0004 is read, and if the data at this address is 0xFFFF.FFFF, the ROM is mapped to address 0x0000.0000 and execution continues out of the ROM Boot Loader.
- **4.** If there is data at address 0x0000.0004 that is not 0xFFFF.FFF, the stack pointer (**SP**) is loaded from Flash memory at address 0x0000.0000 and the program counter (**PC**) is loaded from address 0x0000.0004. The user application begins executing.

For example, if the **BOOTCFG** register is written and committed with the value of 0x0000.3C01, then PB7 is examined at reset to determine if the ROM Boot Loader should be executed. If PB7 is Low, the core unconditionally begins executing the ROM boot loader. If PB7 is High, then the application in Flash memory is executed if the reset vector at location 0x0000.0004 is not 0xFFFF.FFFF. Otherwise, the ROM boot loader is executed.

5.2.2.2 Power-On Reset (POR)

Note: The JTAG controller can only be reset by the power-on reset.

The internal Power-On Reset (POR) circuit monitors the power supply voltage (V_{DD}) and generates a reset signal to all of the internal logic including JTAG when the power supply ramp reaches a threshold value (V_{TH}). The microcontroller must be operating within the specified operating parameters when the on-chip power-on reset pulse is complete (see "Power and Brown-Out" on page 1383). For applications that require the use of an external reset signal to hold the microcontroller in reset longer than the internal POR, the $\overline{\text{RST}}$ input may be used as discussed in "External $\overline{\text{RST}}$ Pin" on page 218.

The Power-On Reset sequence is as follows:

- 1. The microcontroller waits for internal POR to go inactive.
- 2. The internal reset is released and the core loads from memory the initial stack pointer, the initial program counter, and the first instruction designated by the program counter, and then begins execution.


The internal POR is only active on the initial power-up of the microcontroller and when the microcontroller wakes from hibernation. The Power-On Reset timing is shown in "Power and Brown-Out" on page 1383.

5.2.2.3 External RST Pin

Note: It is recommended that the trace for the $\overline{\mathtt{RST}}$ signal must be kept as short as possible. Be sure to place any components connected to the $\overline{\mathtt{RST}}$ signal as close to the microcontroller as possible.

If the application only uses the internal POR circuit, the $\overline{\mbox{RST}}$ input must be connected to the power supply (V_{DD}) through an optional pull-up resistor (0 to 100K Ω) as shown in Figure 5-1 on page 219. The $\overline{\mbox{RST}}$ input has filtering which requires a minimum pulse width in order for the reset pulse to be recognized, see Table 24-11 on page 1388.

Figure 5-1. Basic RST Configuration




 R_{PU} = 0 to 100 k Ω

The external reset pin (\overline{RST}) resets the microcontroller including the core and all the on-chip peripherals. The external reset sequence is as follows:

- 1. The external reset pin (\overline{RST}) is asserted for the duration specified by T_{MIN} and then de-asserted (see "Reset" on page 1388).
- 2. The internal reset is released and the core loads from memory the initial stack pointer, the initial program counter, and the first instruction designated by the program counter, and then begins execution.

To improve noise immunity and/or to delay reset at power up, the \overline{RST} input may be connected to an RC network as shown in Figure 5-2 on page 219.

Figure 5-2. External Circuitry to Extend Power-On Reset




 $R_{PU} = 1 k\Omega$ to 100 $k\Omega$

 $C_1 = 1 \text{ nF to } 10 \mu\text{F}$

If the application requires the use of an external reset switch, Figure 5-3 on page 220 shows the proper circuitry to use.

Figure 5-3. Reset Circuit Controlled by Switch



Typical $R_{PU} = 10 \text{ k}\Omega$

Typical $R_S = 470 \Omega$

 $C_1 = 10 \text{ nF}$

The R_{PLI} and C₁ components define the power-on delay.

The external reset timing is shown in Figure 24-11 on page 1389.

5.2.2.4 Brown-Out Reset (BOR)

The microcontroller provides a brown-out detection circuit that triggers if any of the following occur:

- V_{DD} under BOR0. The external V_{DD} supply voltage is below the specified V_{DD} BOR0 value. The trigger value is the highest V_{DD} voltage level for BOR0.
- V_{DD} under BOR1. The external V_{DD} supply voltage is below the specified V_{DD} BOR1 value. The trigger value is the highest V_{DD} voltage level for BOR1.

The application can identify that a BOR event caused a reset by reading the **Reset Cause (RESC)** register. When a brown-out condition is detected, the default condition is to generate a reset. The BOR events can also be programmed to generate an interrupt by clearing the BORO bit or BOR1 bit in the **Power-On and Brown-Out Reset Control (PBORCTL)** register.

The brown-out reset sequence is as follows:

- When V_{DD} drops below V_{BORnTH}, an internal BOR condition is set. Please refer to "Power and Brown-Out" on page 1383 for V_{BORnTH} value.
- 2. If the BOR condition exists, an internal reset is asserted.
- The internal reset is released and the microcontroller fetches and loads the initial stack pointer, the initial program counter, the first instruction designated by the program counter, and begins execution.

The result of a brown-out reset is equivalent to that of an assertion of the external $\overline{\mathtt{RST}}$ input, and the reset is held active until the proper V_{DD} level is restored. The **RESC** register can be examined in the reset interrupt handler to determine if a Brown-Out condition was the cause of the reset, thus allowing software to determine what actions are required to recover.

The internal Brown-Out Reset timing is shown in "Power and Brown-Out" on page 1383.

5.2.2.5 Software Reset

Software can reset a specific peripheral or generate a reset to the entire microcontroller.

Peripherals can be individually reset by software via peripheral-specific reset registers available beginning at System Control offset 0x500 (for example the **Watchdog Timer Software Reset (SRWD)** register). If the bit position corresponding to a peripheral is set and subsequently cleared, the peripheral is reset.

The entire microcontroller, including the core, can be reset by software by setting the SYSRESREQ bit in the **Application Interrupt and Reset Control (APINT)** register. The software-initiated system reset sequence is as follows:

- 1. A software microcontroller reset is initiated by setting the SYSRESREQ bit.
- 2. An internal reset is asserted.
- 3. The internal reset is deasserted and the microcontroller loads from memory the initial stack pointer, the initial program counter, and the first instruction designated by the program counter, and then begins execution.

The core only can be reset by software by setting the VECTRESET bit in the **APINT** register. The software-initiated core reset sequence is as follows:

- 1. A core reset is initiated by setting the VECTRESET bit.
- 2. An internal reset is asserted.
- **3.** The internal reset is deasserted and the microcontroller loads from memory the initial stack pointer, the initial program counter, and the first instruction designated by the program counter, and then begins execution.

The software-initiated system reset timing is shown in Figure 24-12 on page 1389.

5.2.2.6 Watchdog Timer Reset

The Watchdog Timer module's function is to prevent system hangs. The LM4F232H5QC microcontroller has two Watchdog Timer modules in case one watchdog clock source fails. One watchdog is run off the system clock and the other is run off the Precision Internal Oscillator (PIOSC). Each module operates in the same manner except that because the PIOSC watchdog timer module is in a different clock domain, register accesses must have a time delay between them. The watchdog timer can be configured to generate an interrupt or a non-maskable interrupt to the microcontroller on its first time-out and to generate a reset on its second time-out.

After the watchdog's first time-out event, the 32-bit watchdog counter is reloaded with the value of the **Watchdog Timer Load (WDTLOAD)** register and resumes counting down from that value. If the timer counts down to zero again before the first time-out interrupt is cleared, and the reset signal has been enabled, the watchdog timer asserts its reset signal to the microcontroller. The watchdog timer reset sequence is as follows:

- 1. The watchdog timer times out for the second time without being serviced.
- 2. An internal reset is asserted.
- 3. The internal reset is released and the microcontroller loads from memory the initial stack pointer, the initial program counter, and the first instruction designated by the program counter, and then begins execution.

For more information on the Watchdog Timer module, see "Watchdog Timers" on page 774.

The watchdog reset timing is shown in Figure 24-13 on page 1389.

5.2.3 Non-Maskable Interrupt

The microcontroller has four sources of non-maskable interrupt (NMI):

- The assertion of the NMI signal
- A main oscillator verification error
- The NMISET bit in the Interrupt Control and State (INTCTRL) register in the Cortex[™]-M4F (see page 164).
- The Watchdog module time-out interrupt when the INTTYPE bit in the Watchdog Control (WDTCTL) register is set (see page 780).

Software must check the cause of the interrupt in order to distinguish among the sources.

5.2.3.1 NMI Pin

The NMI signal is an alternate function for either GPIO port pin PD7 or PF0. The alternate function must be enabled in the GPIO for the signal to be used as an interrupt, as described in "General-Purpose Input/Outputs (GPIOs)" on page 646. Note that enabling the NMI alternate function requires the use of the GPIO lock and commit function just like the GPIO port pins associated with JTAG/SWD functionality, see page 684. The active sense of the NMI signal is High; asserting the enabled NMI signal above V_{IH} initiates the NMI interrupt sequence.

5.2.3.2 Main Oscillator Verification Failure

The LM4F232H5QC microcontroller provides a main oscillator verification circuit that generates an error condition if the oscillator is running too fast or too slow. If the main oscillator verification circuit is enabled and a failure occurs, either a power-on reset is generated and control is transferred to the NMI handler, or an interrupt is generated. The MOSCIM bit in the MOSCCTL register determines which action occurs. In either case, the system clock source is automatically switched to the PIOSC. If a MOSC failure reset occurs, the NMI handler is used to address the main oscillator verification failure because the necessary code can be removed from the general reset handler, speeding up reset processing. The detection circuit is enabled by setting the CVAL bit in the Main Oscillator Control (MOSCCTL) register. The main oscillator verification error is indicated in the main oscillator fail status (MOSCFAIL) bit in the Reset Cause (RESC) register. The main oscillator verification circuit action is described in more detail in "Main Oscillator Verification Circuit" on page 230.

5.2.4 Power Control

The Stellaris microcontroller provides an integrated LDO regulator that is used to provide power to the majority of the microcontroller's internal logic. Figure 5-4 shows the power architecture.

An external LDO may not be used.

Note: VDDA must be supplied with a voltage that meets the specification in Table 24-5 on page 1378, or the microcontroller does not function properly. VDDA is the supply for all of the analog circuitry on the device, including the clock circuitry.




Figure 5-4. Power Architecture

5.2.5 Clock Control

System control determines the control of clocks in this part.

5.2.5.1 Fundamental Clock Sources

There are multiple clock sources for use in the microcontroller:

- Precision Internal Oscillator (PIOSC). The precision internal oscillator is an on-chip clock source that is the clock source the microcontroller uses during and following POR. It does not require the use of any external components and provides a clock that is 16 MHz ±1% at room temperature and ±3% across temperature. The PIOSC allows for a reduced system cost in applications that require an accurate clock source. If the main oscillator is required, software must enable the main oscillator following reset and allow the main oscillator to stabilize before changing the clock reference. If the Hibernation Module clock source is a 32.768-kHz oscillator, the precision internal oscillator can be trimmed by software based on a reference clock for increased accuracy. Regardless of whether or not the PIOSC is the source for the system clock, the PIOSC can be configured to be the source for the ADC clock as well as the baud clock for the UART and SSI, see "System Control" on page 231.
- Main Oscillator (MOSC). The main oscillator provides a frequency-accurate clock source by one of two means: an external single-ended clock source is connected to the OSC0 input pin, or

an external crystal is connected across the OSC0 input and OSC1 output pins. If the PLL is being used, the crystal value must be one of the supported frequencies between 5 MHz to 25 MHz (inclusive). If the PLL is not being used, the crystal may be any one of the supported frequencies between 4 MHz to 25 MHz. The single-ended clock source range is as specified in Table 24-13 on page 1391. The supported crystals are listed in the XTAL bit field in the RCC register (see page 255). Note that the MOSC provides the clock source for the USB PLL and must be connected to a crystal or an oscillator.

- Low-Frequency Internal Oscillator (LFIOSC). The low-frequency internal oscillator is intended for use during Deep-Sleep power-saving modes. The frequency can have wide variations; refer to "Low-Frequency Internal Oscillator (LFIOSC) Specifications" on page 1392 for more details. This power-savings mode benefits from reduced internal switching and also allows the MOSC to be powered down.
- **Hibernation Module Clock Source.** The Hibernation module is clocked by a 32.768-kHz oscillator connected to the xosco pin. The 32.768-kHz oscillator can be used for the system clock, thus eliminating the need for an additional crystal or oscillator. The Hibernation module clock source is intended to provide the system with a real-time clock source and may also provide an accurate source of Deep-Sleep or Hibernate mode power savings.

The internal system clock (SysClk), is derived from any of the above sources plus two others: the output of the main internal PLL and the precision internal oscillator divided by four (4 MHz \pm 1%). The frequency of the PLL clock reference must be in the range of 5 MHz to 25 MHz (inclusive). Table 5-3 on page 224 shows how the various clock sources can be used in a system.

Table 5-	Clock	Source	Options
----------	-------------------------	--------	----------------

Clock Source	Drive PLL?	Drive PLL?		Clk?
Precision Internal Oscillator	Yes	BYPASS = 0, OSCSRC = 0x1	Yes	BYPASS = 1, OSCSRC = 0x1
Precision Internal Oscillator divide by 4 (4 MHz ± 1%)	No	-	Yes	BYPASS = 1, OSCSRC = 0x2
Main Oscillator	Yes	BYPASS = 0, OSCSRC = 0x0	Yes	BYPASS = 1, OSCSRC = 0x0
Low-Frequency Internal Oscillator (LFIOSC)	No	-	Yes	BYPASS = 1, OSCSRC = 0x3
Hibernation Module 32.768-kHz Oscillator	No	-	Yes	BYPASS = 1, OSCSRC2 = 0x7

5.2.5.2 Clock Configuration

The Run-Mode Clock Configuration (RCC) and Run-Mode Clock Configuration 2 (RCC2) registers provide control for the system clock. The RCC2 register is provided to extend fields that offer additional encodings over the RCC register. When used, the RCC2 register field values are used by the logic over the corresponding field in the RCC register. In particular, RCC2 provides for a larger assortment of clock configuration options. These registers control the following clock functionality:

- Source of clocks in sleep and deep-sleep modes
- System clock derived from PLL or other clock source
- Enabling/disabling of oscillators and PLL

- Clock divisors
- Crystal input selection

Important: Write the **RCC** register prior to writing the **RCC2** register. If a subsequent write to the **RCC** register is required, include another register access after writing the **RCC** register and before writing the **RCC2** register.

When transitioning the system clock configuration to use the MOSC as the fundamental clock source, the MOSCDIS bit must be set prior to reselecting the MOSC or an undefined system clock configuration can sporadically occur.

The configuration of the system clock must not be changed while an EEPROM operation is in process. Software must wait until the WORKING bit in the **EEPROM Done Status** (**EEDONE**) register is clear before making any changes to the system clock.

Figure 5-5 shows the logic for the main clock tree. The peripheral blocks are driven by the system clock signal and can be individually enabled/disabled. The ADC clock signal can be selected from the PIOSC, the system clock if the PLL is disabled, or the PLL output divided down to 16 MHz if the PLL is enabled. The PWM clock signal is a synchronous divide of the system clock to provide the PWM circuit with more range (set with PWMDIV in **RCC**).

Note: If the ADC module is not using the PIOSC as the clock source, the system clock must be at least 16 MHz. When the USB module is in operation, MOSC must be the clock source, either with or without using the PLL, and the system clock must be at least 20 MHz.

USB PLL **USB Clock** ÷ 8 (480 MHz) USEPWMDIV a PWMDW^a PWM Clock PWRDN b CS f MOSCDIS^a PLL BYPASS b,d (400 MHz) USESYSDIV a,d **UART Baud Clock** Main OSC DIV400^c ÷ 2 IOSÇDISª System Clock Precision Internal OSC ÷ SYSDIV^e CS1 (16 MHz) ÷ 4 BYPASS b,d PWRDN Internal OSC (30 kHz) SSI Baud Clock ÷ 25 Hibernation OSCSRC^{b,d} OSC (32.768 kHz) CS ADC Clock

Figure 5-5. Main Clock Tree

Note:

- **a.** Control provided by **RCC** register bit/field.
- b. Control provided by RCC register bit/field or RCC2 register bit/field, if overridden with RCC2 register bit USERCC2.
- c. Control provided by RCC2 register bit/field.
- **d.** Also may be controlled by **DSLPCLKCFG** when in deep sleep mode.
- e. Control provided by RCC register SYSDIV field, RCC2 register SYSDIV2 field if overridden with USERCC2 bit, or [SYSDIV2,SYSDIV2LSB] if both USERCC2 and DIV400 bits are set.
- f. Control provided by UARTCC, SSICC, and ADCCC register field.

Communication Clock Sources

In addition to the main clock tree described above, the UART, and SSI modules all have a Clock Control register in the peripheral's register map at offset 0xFC8 that can be used to select the clock source for the module's baud clock. Users can choose between the system clock, which is the default source for the baud clock, and the PIOSC. Note that there may be special considerations when using the PIOSC as the baud clock. For more information, see the Clock Control register description in the chapter describing the operation of the module.

Using the SYSDIV and SYSDIV2 Fields

In the RCC register, the SYSDIV field specifies which divisor is used to generate the system clock from either the PLL output or the oscillator source (depending on how the BYPASS bit in this register is configured). When using the PLL, the VCO frequency of 400 MHz is predivided by 2 before the divisor is applied. Table 5-4 shows how the SYSDIV encoding affects the system clock frequency, depending on whether the PLL is used (BYPASS=0) or another clock source is used (BYPASS=1). The divisor is equivalent to the SYSDIV encoding plus 1. For a list of possible clock sources, see Table 5-3 on page 224.

Table 5-4. Possible System Clock Frequencies Using the SYSDIV Field

SYSDIV	Divisor	Frequency (BYPASS=0)	Frequency (BYPASS=1)	StellarisWare [®] Parameter ^a
0x0	/1	reserved	Clock source frequency/1	SYSCTL_SYSDIV_1
0x1	/2	reserved	Clock source frequency/2	SYSCTL_SYSDIV_2
0x2	/3	66.67 MHz	Clock source frequency/3	SYSCTL_SYSDIV_3
0x3	/4	50 MHz	Clock source frequency/4	SYSCTL_SYSDIV_4
0x4	/5	40 MHz	Clock source frequency/5	SYSCTL_SYSDIV_5
0x5	/6	33.33 MHz	Clock source frequency/6	SYSCTL_SYSDIV_6
0x6	/7	28.57 MHz	Clock source frequency/7	SYSCTL_SYSDIV_7
0x7	/8	25 MHz	Clock source frequency/8	SYSCTL_SYSDIV_8
0x8	/9	22.22 MHz	Clock source frequency/9	SYSCTL_SYSDIV_9
0x9	/10	20 MHz	Clock source frequency/10	SYSCTL_SYSDIV_10
0xA	/11	18.18 MHz	Clock source frequency/11	SYSCTL_SYSDIV_11
0xB	/12	16.67 MHz	Clock source frequency/12	SYSCTL_SYSDIV_12
0xC	/13	15.38 MHz	Clock source frequency/13	SYSCTL_SYSDIV_13
0xD	/14	14.29 MHz	Clock source frequency/14	SYSCTL_SYSDIV_14
0xE	/15	13.33 MHz	Clock source frequency/15	SYSCTL_SYSDIV_15
0xF	/16	12.5 MHz (default)	Clock source frequency/16	SYSCTL_SYSDIV_16

a. This parameter is used in functions such as SysCtlClockSet() in the Stellaris Peripheral Driver Library.

The SYSDIV2 field in the **RCC2** register is 2 bits wider than the SYSDIV field in the **RCC** register so that additional larger divisors up to /64 are possible, allowing a lower system clock frequency for improved Deep Sleep power consumption. When using the PLL, the VCO frequency of 400 MHz is predivided by 2 before the divisor is applied. The divisor is equivalent to the SYSDIV2 encoding plus 1. Table 5-5 shows how the SYSDIV2 encoding affects the system clock frequency, depending on whether the PLL is used (BYPASS2=0) or another clock source is used (BYPASS2=1). For a list of possible clock sources, see Table 5-3 on page 224.

Table 5-5. Examples of Possible System Clock Frequencies Using the SYSDIV2 Field

SYSDIV2	Divisor	Frequency (BYPASS2=0)	Frequency (BYPASS2=1)	StellarisWare Parameter ^a
0x00	/1	reserved	Clock source frequency/1	SYSCTL_SYSDIV_1
0x01	/2	reserved	Clock source frequency/2	SYSCTL_SYSDIV_2
0x02	/3	66.67 MHz	Clock source frequency/3	SYSCTL_SYSDIV_3
0x03	/4	50 MHz	Clock source frequency/4	SYSCTL_SYSDIV_4
0x04	/5	40 MHz	Clock source frequency/5	SYSCTL_SYSDIV_5

Table 5-5. Examples of Possible System Clock Frequencies Using the SYSDIV2 Field (continued)

SYSDIV2	Divisor	Frequency (BYPASS2=0)	Frequency (BYPASS2=1)	StellarisWare Parameter ^a
0x09	/10	20 MHz	Clock source frequency/10	SYSCTL_SYSDIV_10
0x3F	/64	3.125 MHz	Clock source frequency/64	SYSCTL_SYSDIV_64

a. This parameter is used in functions such as SysCtlClockSet() in the Stellaris Peripheral Driver Library.

To allow for additional frequency choices when using the PLL, the DIV400 bit is provided along with the SYSDIV2LSB bit. When the DIV400 bit is set, bit 22 becomes the LSB for SYSDIV2. In this situation, the divisor is equivalent to the (SYSDIV2 encoding with SYSDIV2LSB appended) plus one. Table 5-6 shows the frequency choices when DIV400 is set. When the DIV400 bit is clear, SYSDIV2LSB is ignored, and the system clock frequency is determined as shown in Table 5-5 on page 227.

Table 5-6. Examples of Possible System Clock Frequencies with DIV400=1

SYSDIV2	SYSDIV2LSB	Divisor	Frequency (BYPASS2=0) ^a	StellarisWare Parameter ^b
0x00	reserved	/2	reserved	-
0x01	0	/3	reserved	-
UXUT	1	/4	reserved	-
0x02	0	/5	80 MHz	SYSCTL_SYSDIV_2_5
UXU2	1	/6	66.67 MHz	SYSCTL_SYSDIV_3
000	0	/7	reserved	-
0x03	1	/8	50 MHz	SYSCTL_SYSDIV_4
0x04	0	/9	44.44 MHz	SYSCTL_SYSDIV_4_5
0004	1	/10	40 MHz	SYSCTL_SYSDIV_5
0x3F	0	/127	3.15 MHz	SYSCTL_SYSDIV_63_5
UXJI	1	/128	3.125 MHz	SYSCTL_SYSDIV_64

a. Note that ${\tt DIV400}$ and ${\tt SYSDIV2LSB}$ are only valid when ${\tt BYPASS2=0}$.

5.2.5.3 Precision Internal Oscillator Operation (PIOSC)

The microcontroller powers up with the PIOSC running. If another clock source is desired, the PIOSC must remain enabled as it is used for internal functions.

The PIOSC generates a 16-MHz clock with a $\pm 1\%$ accuracy at room temperatures. Across the extended temperature range, the accuracy is $\pm 3\%$. At the factory, the PIOSC is set to 16 MHz at room temperature, however, the frequency can be trimmed for other voltage or temperature conditions using software in one of three ways:

- Default calibration: clear the UTEN bit and set the UPDATE bit in the Precision Internal Oscillator Calibration (PIOSCCAL) register.
- User-defined calibration: The user can program the UT value to adjust the PIOSC frequency. As the UT value increases, the generated period increases. To commit a new UT value, first set the UTEN bit, then program the UT field, and then set the UPDATE bit. The adjustment finishes within a few clock periods and is glitch free.

b. This parameter is used in functions such as SysCtlClockSet() in the Stellaris Peripheral Driver Library.

■ Automatic calibration using the Hibernation module with a functioning 32.768-kHz clock source: Set the CAL bit in the PIOSCCAL register; the results of the calibration are shown in the RESULT field in the Precision Internal Oscillator Statistic (PIOSCSTAT) register. After calibration is complete, the PIOSC is trimmed using the trimmed value returned in the CT field.

5.2.5.4 Crystal Configuration for the Main Oscillator (MOSC)

The main oscillator supports the use of a select number of crystals from 4 to 25 MHz.

The XTAL bit in the **RCC** register (see page 255) describes the available crystal choices and default programming values.

Software configures the **RCC** register XTAL field with the crystal number. If the PLL is used in the design, the XTAL field value is internally translated to the PLL settings.

5.2.5.5 Main PLL Frequency Configuration

The main PLL is disabled by default during power-on reset and is enabled later by software if required. Software specifies the output divisor to set the system clock frequency and enables the main PLL to drive the output. The PLL operates at 400 MHz, but is divided by two prior to the application of the output divisor, unless the DIV400 bit in the **RCC2** register is set.

To configure the PIOSC to be the clock source for the main PLL, program the OSCRC2 field in the Run-Mode Clock Configuration 2 (RCC2) register to be 0x1.

If the main oscillator provides the clock reference to the main PLL, the translation provided by hardware and used to program the PLL is available for software in the **PLL Frequency n** (**PLLFREQn**) registers (see page 273). The internal translation provides a translation within \pm 1% of the targeted PLL VCO frequency. Table 24-14 on page 1391 shows the actual PLL frequency and error for a given crystal choice.

The Crystal Value field (XTAL) in the **Run-Mode Clock Configuration (RCC)** register (see page 255) describes the available crystal choices and default programming of the **PLLFREQn** registers. Any time the XTAL field changes, the new settings are translated and the internal PLL settings are updated.

5.2.5.6 USB PLL Frequency Configuration

The USB PLL is disabled by default during power-on reset and is enabled later by software. The USB PLL must be enabled and running for proper USB function. The main oscillator is the only clock reference for the USB PLL. The USB PLL is enabled by clearing the USBPWRDN bit of the RCC2 register. The XTAL bit field (Crystal Value) of the RCC register describes the available crystal choices. The main oscillator must be connected to one of the following crystal values in order to correctly generate the USB clock: 5, 6, 8, 10, 12, 16, 18, 20, 24, or 25 MHz. Only these crystals provide the necessary USB PLL VCO frequency to conform with the USB timing specifications.

5.2.5.7 PLL Modes

Both PLLs have two modes of operation: Normal and Power-Down

- Normal: The PLL multiplies the input clock reference and drives the output.
- Power-Down: Most of the PLL internal circuitry is disabled and the PLL does not drive the output.

The modes are programmed using the RCC/RCC2 register fields (see page 255 and page 263).

5.2.5.8 PLL Operation

If a PLL configuration is changed, the PLL output frequency is unstable until it reconverges (relocks) to the new setting. The time between the configuration change and relock is T_{READY} (see Table 24-13 on page 1391). During the relock time, the affected PLL is not usable as a clock reference. Software can poll the LOCK bit in the **PLL Status (PLLSTAT)** register to determine when the PLL has locked.

Either PLL is changed by one of the following:

- Change to the XTAL value in the RCC register—writes of the same value do not cause a relock.
- Change in the PLL from Power-Down to Normal mode.

A counter clocked by the system clock is used to measure the T_{READY} requirement. The down counter is set to 0x200 if the PLL is powering up. If the M or N values in the **PLLFREQn** registers are changed, the counter is set to 0xC0. Hardware is provided to keep the PLL from being used as a system clock until the T_{READY} condition is met after one of the two changes above. It is the user's responsibility to have a stable clock source (like the main oscillator) before the **RCC/RCC2** register is switched to use the PLL.

If the main PLL is enabled and the system clock is switched to use the PLL in one step, the system control hardware continues to clock the microcontroller from the oscillator selected by the RCC/RCC2 register until the main PLL is stable (T_{READY} time met), after which it changes to the PLL. Software can use many methods to ensure that the system is clocked from the main PLL, including periodically polling the PLLLRIS bit in the Raw Interrupt Status (RIS) register, and enabling the PLL Lock interrupt.

The USB PLL is not protected during the lock time (T_{READY}), and software should ensure that the USB PLL has locked before using the interface. Software can use many methods to ensure the T_{READY} period has passed, including periodically polling the USBPLLLRIS bit in the **Raw Interrupt Status (RIS)** register, and enabling the USB PLL Lock interrupt.

5.2.5.9 Main Oscillator Verification Circuit

The clock control includes circuitry to ensure that the main oscillator is running at the appropriate frequency. The circuit monitors the main oscillator frequency and signals if the frequency is outside of the allowable band of attached crystals.

The detection circuit is enabled using the CVAL bit in the **Main Oscillator Control (MOSCCTL)** register. If this circuit is enabled and detects an error, and if the MOSCIM bit in the **MOSCCTL** register is clear, then the following sequence is performed by the hardware:

- 1. The MOSCFAIL bit in the Reset Cause (RESC) register is set.
- 2. The system clock is switched from the main oscillator to the PIOSC.
- 3. An internal power-on reset is initiated.
- **4.** Reset is de-asserted and the processor is directed to the NMI handler during the reset sequence.

if the MOSCIM bit in the **MOSCCTL** register is set, then the following sequence is performed by the hardware:

1. The system clock is switched from the main oscillator to the PIOSC.

2. The MOFRIS bit in the RIS register is set to indicate a MOSC failure.

5.2.6 System Control

For power-savings purposes, the peripheral-specific **RCGCx**, **SCGCx**, and **DCGCx** registers (for example, **RCGCWD**) control the clock gating logic for that peripheral or block in the system while the microcontroller is in Run, Sleep, and Deep-Sleep mode, respectively. These registers are located in the System Control register map starting at offsets 0x600, 0x700, and 0x800, respectively. There must be a delay of 3 system clocks after a peripheral module clock is enabled in the **RCGC** register before any module registers are accessed.

Important: To support legacy software, the RCGCn, SCGCn, and DCGCn registers are available at offsets 0x100 - 0x128. A write to any of these legacy registers also writes the corresponding bit in the peripheral-specific RCGCx, SCGCx, and DCGCx registers. Software must use the peripheral-specific registers to support modules that are not present in the legacy registers. It is recommended that new software use the new registers and not rely on legacy operation.

If software uses a peripheral-specific register to write a legacy peripheral (such as TIMER0), the write causes proper operation, but the value of that bit is not reflected in the legacy register. Any bits that are changed by writing to a legacy register can be read back correctly with a read of the legacy register. If software uses both legacy and peripheral-specific register accesses, the peripheral-specific registers must be accessed by read-modify-write operations that affect only peripherals that are not present in the legacy registers. In this manner, both the peripheral-specific and legacy registers have coherent information.

There are four levels of operation for the microcontroller defined as:

- Run mode
- Sleep mode
- Deep-Sleep mode
- Hibernate mode

The following sections describe the different modes in detail.

Caution – If the Cortex-M4F Debug Access Port (DAP) has been enabled, and the device wakes from a low power sleep or deep-sleep mode, the core may start executing code before all clocks to peripherals have been restored to their Run mode configuration. The DAP is usually enabled by software tools accessing the JTAG or SWD interface when debugging or flash programming. If this condition occurs, a Hard Fault is triggered when software accesses a peripheral with an invalid clock.

A software delay loop can be used at the beginning of the interrupt routine that is used to wake up a system from a WFI (Wait For Interrupt) instruction. This stalls the execution of any code that accesses a peripheral register that might cause a fault. This loop can be removed for production software as the DAP is most likely not enabled during normal execution.

Because the DAP is disabled by default (power on reset), the user can also power cycle the device. The DAP is not enabled unless it is enabled through the JTAG or SWD interface.

5.2.6.1 Run Mode

In Run mode, the microcontroller actively executes code. Run mode provides normal operation of the processor and all of the peripherals that are currently enabled by the the peripheral-specific **RCGC** registers. The system clock can be any of the available clock sources including the PLL.

5.2.6.2 Sleep Mode

In Sleep mode, the clock frequency of the active peripherals is unchanged, but the processor and the memory subsystem are not clocked and therefore no longer execute code. Sleep mode is entered by the Cortex-M4F core executing a WFI (Wait for Interrupt) instruction. Any properly configured interrupt event in the system brings the processor back into Run mode. See "Power Management" on page 118 for more details.

Peripherals are clocked that are enabled in the peripheral-specific **SCGC** registers when auto-clock gating is enabled (see the **RCC** register) or the the peripheral-specific **RCGC** registers when the auto-clock gating is disabled. The system clock has the same source and frequency as that during Run mode.

Important: Before executing the WFI instruction, software must confirm that the EEPROM is not busy by checking to see that the WORKING bit in the **EEPROM Done Status (EEDONE)** register is clear.

5.2.6.3 Deep-Sleep Mode

In Deep-Sleep mode, the clock frequency of the active peripherals may change (depending on the Run mode clock configuration) in addition to the processor clock being stopped. An interrupt returns the microcontroller to Run mode from one of the sleep modes; the sleep modes are entered on request from the code. Deep-Sleep mode is entered by first setting the SLEEPDEEP bit in the **System Control (SYSCTRL)** register (see page 170) and then executing a WFI instruction. Any properly configured interrupt event in the system brings the processor back into Run mode. See "Power Management" on page 118 for more details.

The Cortex-M4F processor core and the memory subsystem are not clocked in Deep-Sleep mode. Peripherals are clocked that are enabled in the the peripheral-specific **DCGC** registers when auto-clock gating is enabled (see the **RCC** register) or the peripheral-specific **RCGC** registers when auto-clock gating is disabled. The system clock source is specified in the **DSLPCLKCFG** register. When the **DSLPCLKCFG** register is used, the internal oscillator source is powered up, if necessary, and other clocks are powered down. If the PLL is running at the time of the WFI instruction, hardware powers the PLL down and overrides the SYSDIV field of the active **RCC/RCC2** register, to be determined by the DSDIVORIDE setting in the **DSLPCLKCFG** register, up to /16 or /64 respectively. USB PLL is not powered down by execution of WFI instruction. When the Deep-Sleep exit event occurs, hardware brings the system clock back to the source and frequency it had at the onset of Deep-Sleep mode before enabling the clocks that had been stopped during the Deep-Sleep duration. If the PIOSC is used as the PLL reference clock source, it may continue to provide the clock during Deep-Sleep. See page 267.

Important: Before executing the WFI instruction, software must confirm that the EEPROM is not busy by checking to see that the WORKING bit in the **EEPROM Done Status (EEDONE)** register is clear.

To provide the lowest possible Deep-Sleep power consumption as well the ability to wake the processor from a peripheral without reconfiguring the peripheral for a change in clock, some of the communications modules have a Clock Control register at offset 0xFC8 in the module register space. The CS field in the Clock Control register allows the user to select the PIOSC as the clock source

for the module's baud clock. When the microcontroller enters Deep-Sleep mode, the PIOSC becomes the source for the module clock as well, which allows the transmit and receive FIFOs to continue operation while the part is in Deep-Sleep. Figure 5-6 on page 233 shows how the clocks are selected.




Figure 5-6. Module Clock Selection

5.2.6.4 Hibernate Mode

System Clock

In this mode, the power supplies are turned off to the main part of the microcontroller and only the Hibernation module's circuitry is active. An external wake event or RTC event is required to bring the microcontroller back to Run mode. The Cortex-M4F processor and peripherals outside of the Hibernation module see a normal "power on" sequence and the processor starts running code. Software can determine if the microcontroller has been restarted from Hibernate mode by inspecting the Hibernation module registers. For more information on the operation of Hibernate mode, see "Hibernation Module" on page 491.

0

5.3 Initialization and Configuration

The PLL is configured using direct register writes to the RCC/RCC2 register. If the RCC2 register is being used, the USERCC2 bit must be set and the appropriate RCC2 bit/field is used. The steps required to successfully change the PLL-based system clock are:

- 1. Bypass the PLL and system clock divider by setting the BYPASS bit and clearing the USESYS bit in the RCC register, thereby configuring the microcontroller to run off a "raw" clock source and allowing for the new PLL configuration to be validated before switching the system clock to the PLL.
- 2. Select the crystal value (XTAL) and oscillator source (OSCSRC), and clear the PWRDN bit in RCC/RCC2. Setting the XTAL field automatically pulls valid PLL configuration data for the appropriate crystal, and clearing the PWRDN bit powers and enables the PLL and its output.
- 3. Select the desired system divider (SYSDIV) in RCC/RCC2 and set the USESYS bit in RCC. The SYSDIV field determines the system frequency for the microcontroller.
- 4. Wait for the PLL to lock by polling the PLLLRIS bit in the Raw Interrupt Status (RIS) register.
- 5. Enable use of the PLL by clearing the BYPASS bit in RCC/RCC2.

5.4 Register Map

Table 5-7 on page 234 lists the System Control registers, grouped by function. The offset listed is a hexadecimal increment to the register's address, relative to the System Control base address of 0x400F.E000.

Note: Spaces in the System Control register space that are not used are reserved for future or internal use. Software should not modify any reserved memory address.

Additional Flash and ROM registers defined in the System Control register space are described in the "Internal Memory" on page 522.

Table 5-7. System Control Register Map

Offset	Name	Type	Reset	Description	See page
System C	ontrol Registers				
0x000	DID0	RO	-	Device Identification 0	240
0x004	DID1	RO	-	Device Identification 1	242
0x030	PBORCTL	R/W	0x0000.7FFF	Brown-Out Reset Control	244
0x050	RIS	RO	0x0000.0000	Raw Interrupt Status	245
0x054	IMC	R/W	0x0000.0000	Interrupt Mask Control	248
0x058	MISC	R/W1C	0x0000.0000	Masked Interrupt Status and Clear	250
0x05C	RESC	R/W	-	Reset Cause	253
0x060	RCC	R/W	0x078E.3AD1	Run-Mode Clock Configuration	255
0x06C	GPIOHBCTL	R/W	0x0000.7E00	GPIO High-Performance Bus Control	260
0x070	RCC2	R/W	0x07C0.6810	Run-Mode Clock Configuration 2	263
0x07C	MOSCCTL	R/W	0x0000.0000	Main Oscillator Control	266
0x144	DSLPCLKCFG	R/W	0x0780.0000	Deep Sleep Clock Configuration	267
0x14C	SYSPROP	RO	0x0000.1D31	System Properties	269
0x150	PIOSCCAL	R/W	0x0000.0000	Precision Internal Oscillator Calibration	270
0x154	PIOSCSTAT	RO	0x0000.0040	Precision Internal Oscillator Statistics	272
0x160	PLLFREQ0	RO	0x0000.0032	PLL Frequency 0	273
0x164	PLLFREQ1	RO	0x0000.0001	PLL Frequency 1	274
0x168	PLLSTAT	RO	0x0000.0000	PLL Status	275
0x300	PPWD	RO	0x0000.0003	Watchdog Timer Peripheral Present	276
0x304	PPTIMER	RO	0x0000.003F	16/32-Bit General-Purpose Timer Peripheral Present	277
0x308	PPGPIO	RO	0x0000.03FF	General-Purpose Input/Output Peripheral Present	279
0x30C	PPDMA	RO	0x0000.0001	Micro Direct Memory Access Peripheral Present	282
0x314	PPHIB	RO	0x0000.0001	Hibernation Peripheral Present	283

Table 5-7. System Control Register Map (continued)

Offset	Name	Туре	Reset	Description	See page
0x318	PPUART	RO	0x0000.00FF	Universal Asynchronous Receiver/Transmitter Peripheral Present	284
0x31C	PPSSI	RO	0x0000.000F	Synchronous Serial Interface Peripheral Present	286
0x320	PPI2C	RO	0x0000.003F	Inter-Integrated Circuit Peripheral Present	288
0x328	PPUSB	RO	0x0000.0001	Universal Serial Bus Peripheral Present	290
0x334	PPCAN	RO	0x0000.0003	Controller Area Network Peripheral Present	291
0x338	PPADC	RO	0x0000.0003	Analog-to-Digital Converter Peripheral Present	292
0x33C	PPACMP	RO	0x0000.0001	Analog Comparator Peripheral Present	293
0x340	PPPWM	RO	0x0000.0003	Pulse Width Modulator Peripheral Present	294
0x344	PPQEI	RO	0x0000.0003	Quadrature Encoder Interface Peripheral Present	295
0x358	PPEEPROM	RO	0x0000.0001	EEPROM Peripheral Present	296
0x35C	PPWTIMER	RO	0x0000.003F	32/64-Bit Wide General-Purpose Timer Peripheral Present	297
0x500	SRWD	R/W	0x0000.0000	Watchdog Timer Software Reset	299
0x504	SRTIMER	R/W	0x0000.0000	16/32-Bit General-Purpose Timer Software Reset	301
0x508	SRGPIO	R/W	0x0000.0000	General-Purpose Input/Output Software Reset	303
0x50C	SRDMA	R/W	0x0000.0000	Micro Direct Memory Access Software Reset	306
0x514	SRHIB	R/W	0x0000.0000	Hibernation Software Reset	307
0x518	SRUART	R/W	0x0000.0000	Universal Asynchronous Receiver/Transmitter Software Reset	308
0x51C	SRSSI	R/W	0x0000.0000	Synchronous Serial Interface Software Reset	310
0x520	SRI2C	R/W	0x0000.0000	Inter-Integrated Circuit Software Reset	312
0x528	SRUSB	R/W	0x0000.0000	Universal Serial Bus Software Reset	314
0x534	SRCAN	R/W	0x0000.0000	Controller Area Network Software Reset	315
0x538	SRADC	R/W	0x0000.0000	Analog-to-Digital Converter Software Reset	317
0x53C	SRACMP	R/W	0x0000.0000	Analog Comparator Software Reset	319
0x540	SRPWM	R/W	0x0000.0000	Pulse Width Modulator Software Reset	320
0x544	SRQEI	R/W	0x0000.0000	Quadrature Encoder Interface Software Reset	322
0x558	SREEPROM	R/W	0x0000.0000	EEPROM Software Reset	324
0x55C	SRWTIMER	R/W	0x0000.0000	32/64-Bit Wide General-Purpose Timer Software Reset	325
0x600	RCGCWD	R/W	0x0000.0000	Watchdog Timer Run Mode Clock Gating Control	327
0x604	RCGCTIMER	R/W	0x0000.0000	16/32-Bit General-Purpose Timer Run Mode Clock Gating Control	328

Table 5-7. System Control Register Map (continued)

Offset	Name	Туре	Reset	Description	See page
0x608	RCGCGPIO	R/W	0x0000.0000	General-Purpose Input/Output Run Mode Clock Gating Control	330
0x60C	RCGCDMA	R/W	0x0000.0000	Micro Direct Memory Access Run Mode Clock Gating Control	333
0x614	RCGCHIB	R/W	0x0000.0001	Hibernation Run Mode Clock Gating Control	334
0x618	RCGCUART	R/W	0x0000.0000	Universal Asynchronous Receiver/Transmitter Run Mode Clock Gating Control	335
0x61C	RCGCSSI	R/W	0x0000.0000	Synchronous Serial Interface Run Mode Clock Gating Control	337
0x620	RCGCI2C	R/W	0x0000.0000	Inter-Integrated Circuit Run Mode Clock Gating Control	339
0x628	RCGCUSB	R/W	0x0000.0000	Universal Serial Bus Run Mode Clock Gating Control	341
0x634	RCGCCAN	R/W	0x0000.0000	Controller Area Network Run Mode Clock Gating Control	342
0x638	RCGCADC	R/W	0x0000.0000	Analog-to-Digital Converter Run Mode Clock Gating Control	343
0x63C	RCGCACMP	R/W	0x0000.0000	Analog Comparator Run Mode Clock Gating Control	344
0x640	RCGCPWM	R/W	0x0000.0000	Pulse Width Modulator Run Mode Clock Gating Control	345
0x644	RCGCQEI	R/W	0x0000.0000	Quadrature Encoder Interface Run Mode Clock Gating Control	346
0x658	RCGCEEPROM	R/W	0x0000.0000	EEPROM Run Mode Clock Gating Control	347
0x65C	RCGCWTIMER	R/W	0x0000.0000	32/64-Bit Wide General-Purpose Timer Run Mode Clock Gating Control	348
0x700	SCGCWD	R/W	0x0000.0000	Watchdog Timer Sleep Mode Clock Gating Control	350
0x704	SCGCTIMER	R/W	0x0000.0000	16/32-Bit General-Purpose Timer Sleep Mode Clock Gating Control	351
0x708	SCGCGPIO	R/W	0x0000.0000	General-Purpose Input/Output Sleep Mode Clock Gating Control	353
0x70C	SCGCDMA	R/W	0x0000.0000	Micro Direct Memory Access Sleep Mode Clock Gating Control	356
0x714	SCGCHIB	R/W	0x0000.0001	Hibernation Sleep Mode Clock Gating Control	357
0x718	SCGCUART	R/W	0x0000.0000	Universal Asynchronous Receiver/Transmitter Sleep Mode Clock Gating Control	358
0x71C	SCGCSSI	R/W	0x0000.0000	Synchronous Serial Interface Sleep Mode Clock Gating Control	360
0x720	SCGCI2C	R/W	0x0000.0000	Inter-Integrated Circuit Sleep Mode Clock Gating Control	362
0x728	SCGCUSB	R/W	0x0000.0000	Universal Serial Bus Sleep Mode Clock Gating Control	364
0x734	SCGCCAN	R/W	0x0000.0000	Controller Area Network Sleep Mode Clock Gating Control	365

Table 5-7. System Control Register Map (continued)

0x840 DCGCPWM R/W 0x0000.0000 Pulse Width Modulator Deep-Sleep Mode Clock Gating Control 391	Offset	Name	Туре	Reset	Description	See page
0x744 SCGCPWM R/W 0x0000.0000 Pulse Width Modulator Sleep Mode Clock Gating Control 388 0x744 SCGCQEI R/W 0x0000.0000 Cuadrature Encoder Interface Sleep Mode Clock Gating Control 369 0x758 SCGCEEPROM R/W 0x0000.0000 EEPROM Sleep Mode Clock Gating Control 370 0x75C SCGCWTIMER R/W 0x0000.0000 32/64-Bit Wide General-Purpose Timer Sleep Mode Clock Gating Control 371 0x800 DCGCWD R/W 0x0000.0000 Watchdog Timer Deep-Sleep Mode Clock Gating Control 373 0x804 DCGCTIMER R/W 0x0000.0000 General-Purpose Imput/Output Deep-Sleep Mode Clock Gating Control 374 0x808 DCGCGPIO R/W 0x0000.0000 General-Purpose Input/Output Deep-Sleep Mode Clock Gating Control 376 0x800 DCGCDMA R/W 0x0000.0000 Micro Direct Memory Access Deep-Sleep Mode Clock Gating Control 380 0x814 DCGCHIB R/W 0x0000.0000 Universal Asynchronous Receiver/Transmitter Deep-Sleep Mode Clock Gating Control 381 0x816 DCGCUZE R/W <td< td=""><td>0x738</td><td>SCGCADC</td><td>R/W</td><td>0x0000.0000</td><td></td><td>366</td></td<>	0x738	SCGCADC	R/W	0x0000.0000		366
0x744 SCGCQEI R/W 0x0000.0000 Quadrature Encoder Interface Sleep Mode Clock Gating Control 369 0x758 SCGCEEPROM R/W 0x0000.0000 EEPROM Sleep Mode Clock Gating Control 370 0x75C SCGCWTIMER R/W 0x0000.0000 32/64-Bit Wide General-Purpose Timer Sleep Mode Clock Gating Control 371 0x800 DCGCWD R/W 0x0000.0000 Watchdog Timer Deep-Sleep Mode Clock Gating Control 373 0x804 DCGCTIMER R/W 0x0000.0000 General-Purpose Input/Output Deep-Sleep Mode Clock Gating Control 374 0x80B DCGCGPIO R/W 0x0000.0000 General-Purpose Input/Output Deep-Sleep Mode Clock Gating Control 376 0x80C DCGCDMA R/W 0x0000.0000 Micro Direct Memory Access Deep-Sleep Mode Clock Gating Control 380 0x81b DCGCHIB R/W 0x0000.0000 Universal Asynchronous Receiver/Transmitter Deep-Sleep Mode Clock Gating Control 381 0x81c DCGCSSI R/W 0x0000.0000 Synchronous Serial Interface Deep-Sleep Mode Clock Gating Control 383 0x82a DCGCI2C R/W	0x73C	SCGCACMP	R/W	0x0000.0000	Analog Comparator Sleep Mode Clock Gating Control	367
0x744 SCECUEI RW 0x00000000 Control 369 0x756 SCGCEEPROM RW 0x0000.0000 EEPROM Sleep Mode Clock Gating Control 370 0x75C SCGCWTIMER RW 0x0000.0000 Watchdog Timer Deep-Sleep Mode Clock Gating Control 371 0x800 DCGCWD RW 0x0000.0000 Watchdog Timer Deep-Sleep Mode Clock Gating Control 373 0x804 DCGCTIMER RW 0x0000.0000 General-Purpose Input/Output Deep-Sleep Mode Clock Gating Control 376 0x808 DCGCDMA RW 0x0000.0000 General-Purpose Input/Output Deep-Sleep Mode Clock Gating Control 376 0x814 DCGCHIB RW 0x0000.0000 Hibernation Deep-Sleep Mode Clock Gating Control 380 0x816 DCGCUART RW 0x0000.0000 Universal Asynchronous Receiver/Transmitter Deep-Sleep Mode Clock Gating Control 381 0x820 DCGCSSI RW 0x0000.0000 Inter-Integrated Circuit Deep-Sleep Mode Clock Gating Control 383 0x828 DCGCUSB RW 0x0000.0000 Inter-Integrated Circuit Deep-Sleep Mode Clock Gating Cont	0x740	SCGCPWM	R/W	0x0000.0000	Pulse Width Modulator Sleep Mode Clock Gating Control	368
0x75C SCGCWTIMER R/W 0x0000.0000 32/64-Bit Wide General-Purpose Timer Sleep Mode Clock Gating Control 371 0x800 DCGCWD R/W 0x0000.0000 Watchdog Timer Deep-Sleep Mode Clock Gating Control 373 0x804 DCGCTIMER R/W 0x0000.0000 18/32-Bit General-Purpose Timer Deep-Sleep Mode Clock Gating Control 374 0x808 DCGCGPIO R/W 0x0000.0000 General-Purpose Input/Output Deep-Sleep Mode Clock Gating Control 376 0x80C DCGCDMA R/W 0x0000.0000 Micro Direct Memory Access Deep-Sleep Mode Clock Gating Control 380 0x814 DCGCHIB R/W 0x0000.0001 Hilbernation Deep-Sleep Mode Clock Gating Control 381 0x816 DCGCUART R/W 0x0000.0000 Universal Asynchronous Receiver/Transmitter Deep-Sleep Mode Clock Gating Control 381 0x810 DCGCSSI R/W 0x0000.0000 Inter-Integrated Circuit Deep-Sleep Mode Clock Gating Control 383 0x820 DCGCI2C R/W 0x0000.0000 Universal Serial Bus Deep-Sleep Mode Clock Gating Control 387 0x832 DCGCUSB R/W	0x744	SCGCQEI	R/W	0x0000.0000		369
0X79C SCGCWTIMER R/W 0X0000.0000 Gating Control 371 0x800 DCGCWD R/W 0x0000.0000 Watchdog Timer Deep-Sleep Mode Clock Gating Control 373 0x804 DCGCTIMER R/W 0x0000.0000 18/32-Bit General-Purpose Timer Deep-Sleep Mode Clock Gating Control 374 0x808 DCGCGPIO R/W 0x0000.0000 General-Purpose Input/Output Deep-Sleep Mode Clock Gating Control 376 0x80C DCGCDMA R/W 0x0000.0000 Micro Direct Memory Access Deep-Sleep Mode Clock Gating Control 380 0x814 DCGCHIB R/W 0x0000.0001 Hibernation Deep-Sleep Mode Clock Gating Control 381 0x816 DCGCUART R/W 0x0000.0000 Universal Asynchronous Receiver/Transmitter Deep-Sleep Mode Clock Gating Control 381 0x810 DCGCSSI R/W 0x0000.0000 Synchronous Serial Interface Deep-Sleep Mode Clock Gating Control 383 0x820 DCGCI2C R/W 0x0000.0000 Inter-Integrated Circuit Deep-Sleep Mode Clock Gating Control 387 0x832 DCGCUSB R/W 0x0000.0000	0x758	SCGCEEPROM	R/W	0x0000.0000	EEPROM Sleep Mode Clock Gating Control	370
0x804 DCGCTIMER R/W 0x0000.0000 16/32-Bit General-Purpose Timer Deep-Sleep Mode Clock Gating Control 374 0x808 DCGCGPIO R/W 0x0000.0000 General-Purpose Input/Output Deep-Sleep Mode Clock Gating Control 376 0x80C DCGCDMA R/W 0x0000.0000 Micro Direct Memory Access Deep-Sleep Mode Clock Gating Control 379 0x814 DCGCHIB R/W 0x0000.0001 Hibernation Deep-Sleep Mode Clock Gating Control 380 0x818 DCGCUART R/W 0x0000.0000 Universal Asynchronous Receiver/Transmitter Deep-Sleep Mode Clock Gating Control 381 0x81C DCGCSSI R/W 0x0000.0000 Synchronous Serial Interface Deep-Sleep Mode Clock Gating Control 383 0x820 DCGCI2C R/W 0x0000.0000 Inter-Integrated Circuit Deep-Sleep Mode Clock Gating Control 385 0x828 DCGCUSB R/W 0x0000.0000 Universal Serial Bus Deep-Sleep Mode Clock Gating Control 387 0x834 DCGCCAN R/W 0x0000.0000 Controller Area Network Deep-Sleep Mode Clock Gating Control 388 0x836 DCGCACMP <td< td=""><td>0x75C</td><td>SCGCWTIMER</td><td>R/W</td><td>0x0000.0000</td><td>·</td><td>371</td></td<>	0x75C	SCGCWTIMER	R/W	0x0000.0000	·	371
0x804 DCGCTIMER R/W 0x0000,0000 Clock Gating Control 3/4 0x808 DCGCGPIO R/W 0x0000,0000 General-Purpose Input/Output Deep-Sleep Mode Clock Gating Control 376 0x80C DCGCDMA R/W 0x0000,0000 Micro Direct Memory Access Deep-Sleep Mode Clock Gating Control 379 0x814 DCGCHIB R/W 0x0000,0000 Hibernation Deep-Sleep Mode Clock Gating Control 380 0x818 DCGCUART R/W 0x0000,0000 Universal Asynchronous Receiver/Transmitter Deep-Sleep Mode Clock Gating Control 381 0x81C DCGCSSI R/W 0x0000,0000 Synchronous Serial Interface Deep-Sleep Mode Clock Gating Control 383 0x820 DCGCI2C R/W 0x0000,0000 Universal Serial Bus Deep-Sleep Mode Clock Gating Control 385 0x828 DCGCUSB R/W 0x0000,0000 Universal Serial Bus Deep-Sleep Mode Clock Gating Control 387 0x834 DCGCCAN R/W 0x0000,0000 Control Control 388 0x836 DCGCADC R/W 0x0000,0000 Analog-to-Digital Converter De	0x800	DCGCWD	R/W	0x0000.0000	Watchdog Timer Deep-Sleep Mode Clock Gating Control	373
0x80B DCGCGPIO R/W 0x0000.0000 Gating Control 376 0x80C DCGCDMA R/W 0x0000.0000 Micro Direct Memory Access Deep-Sleep Mode Clock Gating Control 389 0x814 DCGCHIB R/W 0x0000.0000 Hibernation Deep-Sleep Mode Clock Gating Control 380 0x818 DCGCUART R/W 0x0000.0000 Universal Asynchronous Receiver/Transmitter Deep-Sleep Mode Clock Gating Control 381 0x810 DCGCSSI R/W 0x0000.0000 Synchronous Serial Interface Deep-Sleep Mode Clock Gating Control 383 0x820 DCGCI2C R/W 0x0000.0000 Universal Serial Bus Deep-Sleep Mode Clock Gating Control 385 0x828 DCGCUSB R/W 0x0000.0000 Controller Area Network Deep-Sleep Mode Clock Gating Control 388 0x834 DCGCCAN R/W 0x0000.0000 Analog-to-Digital Converter Deep-Sleep Mode Clock Gating Control 389 0x838 DCGCADC R/W 0x0000.0000 Analog-to-Digital Converter Deep-Sleep Mode Clock Gating Control 390 0x840 DCGCACMP R/W 0x0000.0000 Pul	0x804	DCGCTIMER	R/W	0x0000.0000	·	374
0x80C DCGCHIMA R/W 0x0000.0000 Gating Control 3/9 0x814 DCGCHIB R/W 0x0000.0001 Hibernation Deep-Sleep Mode Clock Gating Control 380 0x818 DCGCUART R/W 0x0000.0000 Universal Asynchronous Receiver/Transmitter Deep-Sleep Mode Clock Gating Control 381 0x81C DCGCSSI R/W 0x0000.0000 Synchronous Serial Interface Deep-Sleep Mode Clock Gating Control 383 0x820 DCGCI2C R/W 0x0000.0000 Inter-Integrated Circuit Deep-Sleep Mode Clock Gating Control 385 0x828 DCGCUSB R/W 0x0000.0000 Universal Serial Bus Deep-Sleep Mode Clock Gating Control 387 0x834 DCGCCAN R/W 0x0000.0000 Controller Area Network Deep-Sleep Mode Clock Gating Control 389 0x838 DCGCADC R/W 0x0000.0000 Analog-to-Digital Converter Deep-Sleep Mode Clock Gating Control 389 0x840 DCGCAMP R/W 0x0000.0000 Pulse Width Modulator Deep-Sleep Mode Clock Gating Control 391 0x858 DCGCQEI R/W 0x0000.0000 Quadrature E	0x808	DCGCGPIO	R/W	0x0000.0000		376
0x818 DCGCUART R/W 0x0000.0000 Universal Asynchronous Receiver/Transmitter Deep-Sleep Mode Clock Gating Control 381 0x81C DCGCSSI R/W 0x0000.0000 Synchronous Serial Interface Deep-Sleep Mode Clock Gating Control 383 0x820 DCGCI2C R/W 0x0000.0000 Inter-Integrated Circuit Deep-Sleep Mode Clock Gating Control 385 0x828 DCGCUSB R/W 0x0000.0000 Universal Serial Bus Deep-Sleep Mode Clock Gating Control 387 0x834 DCGCCAN R/W 0x0000.0000 Controller Area Network Deep-Sleep Mode Clock Gating Control 388 0x838 DCGCADC R/W 0x0000.0000 Analog-to-Digital Converter Deep-Sleep Mode Clock Gating Control 389 0x83C DCGCACMP R/W 0x0000.0000 Analog Comparator Deep-Sleep Mode Clock Gating Control 390 0x840 DCGCPWM R/W 0x0000.0000 Pulse Width Modulator Deep-Sleep Mode Clock Gating Control 392 0x858 DCGCQEI R/W 0x0000.0000 Gating Control 393 0x858 DCGCEEPROM R/W 0x0000.0000 EEP	0x80C	DCGCDMA	R/W	0x0000.0000		379
0x81BDCGCDARTR/W0x0000.0000Deep-Sleep Mode Clock Gating Control3810x81CDCGCSSIR/W0x0000.0000Synchronous Serial Interface Deep-Sleep Mode Clock Gating Control3830x820DCGCI2CR/W0x0000.0000Inter-Integrated Circuit Deep-Sleep Mode Clock Gating Control3850x828DCGCUSBR/W0x0000.0000Universal Serial Bus Deep-Sleep Mode Clock Gating Control3870x834DCGCCANR/W0x0000.0000Controller Area Network Deep-Sleep Mode Clock Gating Control3880x838DCGCADCR/W0x0000.0000Analog-to-Digital Converter Deep-Sleep Mode Clock Gating Gating Control3890x83CDCGCACMPR/W0x0000.0000Analog Comparator Deep-Sleep Mode Clock Gating Control3900x840DCGCPWMR/W0x0000.0000Pulse Width Modulator Deep-Sleep Mode Clock Gating Control3910x844DCGCQEIR/W0x0000.0000Quadrature Encoder Interface Deep-Sleep Mode Clock Gating Control3920x858DCGCEPROMR/W0x0000.0000EEPROM Deep-Sleep Mode Clock Gating Control3930x85CDCGCWTIMERR/W0x0000.000032/64-Bit Wide General-Purpose Timer Deep-Sleep Mode Clock Gating Control394	0x814	DCGCHIB	R/W	0x0000.0001	Hibernation Deep-Sleep Mode Clock Gating Control	380
0x81CDCGCI2CR/W0x0000.0000Gating Control0x820DCGCI2CR/W0x0000.0000Inter-Integrated Circuit Deep-Sleep Mode Clock Gating Control3850x828DCGCUSBR/W0x0000.0000Universal Serial Bus Deep-Sleep Mode Clock Gating Control3870x834DCGCCANR/W0x0000.0000Controller Area Network Deep-Sleep Mode Clock Gating Control3880x838DCGCADCR/W0x0000.0000Analog-to-Digital Converter Deep-Sleep Mode Clock Gating Control3890x83CDCGCACMPR/W0x0000.0000Analog Comparator Deep-Sleep Mode Clock Gating Control3900x840DCGCPWMR/W0x0000.0000Pulse Width Modulator Deep-Sleep Mode Clock Gating Control3910x844DCGCQEIR/W0x0000.0000Quadrature Encoder Interface Deep-Sleep Mode Clock Gating Control3920x858DCGCEEPROMR/W0x0000.0000EEPROM Deep-Sleep Mode Clock Gating Control3930x85CDCGCWTIMERR/W0x0000.000032/64-Bit Wide General-Purpose Timer Deep-Sleep Mode Clock Gating Control394	0x818	DCGCUART	R/W	0x0000.0000		381
0x820DCGCI2CR/W0x0000.0000Control0x828DCGCUSBR/W0x0000.0000Universal Serial Bus Deep-Sleep Mode Clock Gating Control3870x834DCGCCANR/W0x0000.0000Controller Area Network Deep-Sleep Mode Clock Gating Control3880x838DCGCADCR/W0x0000.0000Analog-to-Digital Converter Deep-Sleep Mode Clock Gating Control3890x83CDCGCACMPR/W0x0000.0000Analog Comparator Deep-Sleep Mode Clock Gating Control3900x840DCGCPWMR/W0x0000.0000Pulse Width Modulator Deep-Sleep Mode Clock Gating Control3910x844DCGCQEIR/W0x0000.0000Quadrature Encoder Interface Deep-Sleep Mode Clock Gating Control3920x858DCGCEEPROMR/W0x0000.0000EEPROM Deep-Sleep Mode Clock Gating Control3930x85CDCGCWTIMERR/W0x0000.000032/64-Bit Wide General-Purpose Timer Deep-Sleep Mode Clock Gating Control394	0x81C	DCGCSSI	R/W	0x0000.0000		383
0x828DCGCOSBR/W0x0000.0000Control0x834DCGCCANR/W0x0000.0000Controller Area Network Deep-Sleep Mode Clock Gating Control3880x838DCGCADCR/W0x0000.0000Analog-to-Digital Converter Deep-Sleep Mode Clock Gating Control3890x83CDCGCACMPR/W0x0000.0000Analog Comparator Deep-Sleep Mode Clock Gating Control3900x840DCGCPWMR/W0x0000.0000Pulse Width Modulator Deep-Sleep Mode Clock Gating Control3910x844DCGCQEIR/W0x0000.0000Quadrature Encoder Interface Deep-Sleep Mode Clock Gating Control3920x858DCGCEEPROMR/W0x0000.0000EEPROM Deep-Sleep Mode Clock Gating Control3930x85CDCGCWTIMERR/W0x0000.000032/64-Bit Wide General-Purpose Timer Deep-Sleep Mode Clock Gating Control394	0x820	DCGCI2C	R/W	0x0000.0000		385
0x834DCGCANR/W0x0000.0000Control0x838DCGCADCR/W0x0000.0000Analog-to-Digital Converter Deep-Sleep Mode Clock Gating Control3890x83CDCGCACMPR/W0x0000.0000Analog Comparator Deep-Sleep Mode Clock Gating Control3900x840DCGCPWMR/W0x0000.0000Pulse Width Modulator Deep-Sleep Mode Clock Gating Control3910x844DCGCQEIR/W0x0000.0000Quadrature Encoder Interface Deep-Sleep Mode Clock Gating Control3920x858DCGCEEPROMR/W0x0000.0000EEPROM Deep-Sleep Mode Clock Gating Control3930x85CDCGCWTIMERR/W0x0000.000032/64-Bit Wide General-Purpose Timer Deep-Sleep Mode Clock Gating Control394	0x828	DCGCUSB	R/W	0x0000.0000	, ,	387
0x836DCGCADCR/W0x0000.0000Gating Control0x83CDCGCACMPR/W0x0000.0000Analog Comparator Deep-Sleep Mode Clock Gating Control3900x840DCGCPWMR/W0x0000.0000Pulse Width Modulator Deep-Sleep Mode Clock Gating Control3910x844DCGCQEIR/W0x0000.0000Quadrature Encoder Interface Deep-Sleep Mode Clock Gating Control3920x858DCGCEEPROMR/W0x0000.0000EEPROM Deep-Sleep Mode Clock Gating Control3930x85CDCGCWTIMERR/W0x0000.000032/64-Bit Wide General-Purpose Timer Deep-Sleep Mode Clock Gating Control394	0x834	DCGCCAN	R/W	0x0000.0000		388
0x83C DCGCACMP R/W 0x0000.0000 Control 390 0x840 DCGCPWM R/W 0x0000.0000 Pulse Width Modulator Deep-Sleep Mode Clock Gating Control 391 0x844 DCGCQEI R/W 0x0000.0000 Quadrature Encoder Interface Deep-Sleep Mode Clock Gating Control 392 0x858 DCGCEEPROM R/W 0x0000.0000 EEPROM Deep-Sleep Mode Clock Gating Control 393 0x85C DCGCWTIMER R/W 0x0000.0000 32/64-Bit Wide General-Purpose Timer Deep-Sleep Mode Clock Gating Control 394	0x838	DCGCADC	R/W	0x0000.0000		389
0x844 DCGCQEI R/W 0x0000.0000 Quadrature Encoder Interface Deep-Sleep Mode Clock Gating Control 392 0x858 DCGCEEPROM R/W 0x0000.0000 EEPROM Deep-Sleep Mode Clock Gating Control 393 0x85C DCGCWTIMER R/W 0x0000.0000 32/64-Bit Wide General-Purpose Timer Deep-Sleep Mode Clock Gating Control 394	0x83C	DCGCACMP	R/W	0x0000.0000		390
0x854 DCGCGEI R/W 0x0000.0000 Gating Control 0x858 DCGCEPROM R/W 0x0000.0000 EEPROM Deep-Sleep Mode Clock Gating Control 393 0x85C DCGCWTIMER R/W 0x0000.0000 32/64-Bit Wide General-Purpose Timer Deep-Sleep Mode Clock Gating Control 394	0x840	DCGCPWM	R/W	0x0000.0000		391
0x85C DCGCWTIMER R/W 0x0000.0000 32/64-Bit Wide General-Purpose Timer Deep-Sleep Mode Clock Gating Control 394	0x844	DCGCQEI	R/W	0x0000.0000	i i i	392
UX85C DCGCWTIMER R/W UX0000.0000 Clock Gating Control 394	0x858	DCGCEEPROM	R/W	0x0000.0000	EEPROM Deep-Sleep Mode Clock Gating Control	393
0xA00 PRWD RO 0x0000.0000 Watchdog Timer Peripheral Ready 396	0x85C	DCGCWTIMER	R/W	0x0000.0000		394
	0xA00	PRWD	RO	0x0000.0000	Watchdog Timer Peripheral Ready	396

Table 5-7. System Control Register Map (continued)

Offset	Name	Туре	Reset	Description	See page
0xA04	PRTIMER	RO	0x0000.0000	16/32-Bit General-Purpose Timer Peripheral Ready	397
0xA08	PRGPIO	RO	0x0000.0000	General-Purpose Input/Output Peripheral Ready	399
0xA0C	PRDMA	RO	0x0000.0000	Micro Direct Memory Access Peripheral Ready	401
0xA14	PRHIB	RO	0x0000.0001	Hibernation Peripheral Ready	402
0xA18	PRUART	RO	0x0000.0000	Universal Asynchronous Receiver/Transmitter Peripheral Ready	403
0xA1C	PRSSI	RO	0x0000.0000	Synchronous Serial Interface Peripheral Ready	405
0xA20	PRI2C	RO	0x0000.0000	Inter-Integrated Circuit Peripheral Ready	407
0xA28	PRUSB	RO	0x0000.0000	Universal Serial Bus Peripheral Ready	409
0xA34	PRCAN	RO	0x0000.0000	Controller Area Network Peripheral Ready	410
0xA38	PRADC	RO	0x0000.0000	Analog-to-Digital Converter Peripheral Ready	411
0xA3C	PRACMP	RO	0x0000.0000	Analog Comparator Peripheral Ready	412
0xA40	PRPWM	RO	0x0000.0000	Pulse Width Modulator Peripheral Ready	413
0xA44	PRQEI	RO	0x0000.0000	Quadrature Encoder Interface Peripheral Ready	414
0xA58	PREEPROM	RO	0x0000.0000	EEPROM Peripheral Ready	415
0xA5C	PRWTIMER	RO	0x0000.0000	32/64-Bit Wide General-Purpose Timer Peripheral Ready	416
System C	ontrol Legacy Registers	I			
0x008	DC0	RO	0x007F.007F	Device Capabilities 0	418
0x010	DC1	RO	0x1333.2FFF	Device Capabilities 1	420
0x014	DC2	RO	0x070F.F337	Device Capabilities 2	423
0x018	DC3	RO	0xBFFF.FFFF	Device Capabilities 3	426
0x01C	DC4	RO	0x0004.F1FF	Device Capabilities 4	430
0x020	DC5	RO	0x0F30.00FF	Device Capabilities 5	433
0x024	DC6	RO	0x0000.0013	Device Capabilities 6	435
0x028	DC7	RO	0xFFFF.FFFF	Device Capabilities 7	436
0x02C	DC8	RO	0xFFFF.FFFF	Device Capabilities 8	439
0x040	SRCR0	RO	0x0000.0000	Software Reset Control 0	442
0x044	SRCR1	RO	0x0000.0000	Software Reset Control 1	444
0x048	SRCR2	RO	0x0000.0000	Software Reset Control 2	447
0x100	RCGC0	RO	0x0000.0040	Run Mode Clock Gating Control Register 0	449
0x104	RCGC1	RO	0x0000.0000	Run Mode Clock Gating Control Register 1	453
0x108	RCGC2	RO	0x0000.0000	Run Mode Clock Gating Control Register 2	457

Table 5-7. System Control Register Map (continued)

Offset	Name	Туре	Reset	Description	See page
0x110	SCGC0	RO	0x0000.0040	Sleep Mode Clock Gating Control Register 0	460
0x114	SCGC1	RO	0x0000.0000	Sleep Mode Clock Gating Control Register 1	463
0x118	SCGC2	RO	0x0000.0000	Sleep Mode Clock Gating Control Register 2	467
0x120	DCGC0	RO	0x0000.0040	Deep Sleep Mode Clock Gating Control Register 0	470
0x124	DCGC1	RO	0x0000.0000	Deep-Sleep Mode Clock Gating Control Register 1	473
0x128	DCGC2	RO	0x0000.0000	Deep Sleep Mode Clock Gating Control Register 2	477
0x190	DC9	RO	0x00FF.00FF	Device Capabilities 9	480
0x1A0	NVMSTAT	RO	0x0000.0001	Non-Volatile Memory Information	482

5.5 System Control Register Descriptions


All addresses given are relative to the System Control base address of 0x400F.E000. Registers provided for legacy software support only are listed in "System Control Legacy Register Descriptions" on page 417.

Register 1: Device Identification 0 (DID0), offset 0x000

This register identifies the version of the microcontroller. Each microcontroller is uniquely identified by the combined values of the CLASS field in the **DID0** register and the PARTNO field in the **DID1** register.

Device Identification 0 (DID0)

Base 0x400F.E000 Offset 0x000 Type RO, reset -



Bit/Field	Name	Туре	Reset	Description
31	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
30:28	VER	RO	0x01	DID0 Version
				This field defines the DID0 register format version. The version number is numeric. The value of the VER field is encoded as follows (all other encodings are reserved):
				Value Description
				0x1 Second version of the DID0 register format.
27:24	reserved	RO	0x08	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
23:16	CLASS	RO	0x05	Device Class

The CLASS field value identifies the internal design from which all mask sets are generated for all microcontrollers in a particular product line. The CLASS field value is changed for new product lines, for changes in fab process (for example, a remap or shrink), or any case where the MAJOR or MINOR fields require differentiation from prior microcontrollers. The value of the CLASS field is encoded as follows (all other encodings are reserved):

Value Description

0x05 Stellaris® Blizzard-class microcontrollers

Bit/Field	Name	Туре	Reset	Description
15:8	MAJOR	RO	-	Major Revision This field specifies the major revision number of the microcontroller. The major revision reflects changes to base layers of the design. The major revision number is indicated in the part number as a letter (A for first revision, B for second, and so on). This field is encoded as follows:
				Value Description
				0x0 Revision A (initial device)
				0x1 Revision B (first base layer revision)
				0x2 Revision C (second base layer revision)
				and so on.
7:0	MINOR	RO	-	Minor Revision
				This field specifies the minor revision number of the microcontroller. The minor revision reflects changes to the metal layers of the design. The MINOR field value is reset when the MAJOR field is changed. This field is numeric and is encoded as follows:
				Value Description
				0x0 Initial device, or a major revision update.
				0x1 First metal layer change.
				0x2 Second metal layer change.
				and so on.

February 20, 2013 241

Register 2: Device Identification 1 (DID1), offset 0x004

This register identifies the device family, part number, temperature range, pin count, and package type. Each microcontroller is uniquely identified by the combined values of the CLASS field in the **DID0** register and the PARTNO field in the **DID1** register.

Device Identification 1 (DID1)


Name

Type

Reset

Base 0x400F.E000 Offset 0x004 Type RO, reset -

Bit/Field



31:28	VER	RO	0x1	DID1 Version
				This field defines the DID1 register format version. The version number is numeric. The value of the VER field is encoded as follows (all other encodings are reserved):

Description

Value Description

0x0 Initial **DID1** register format definition, indicating a Stellaris LM3Snnn device.

0x1 Second version of the **DID1** register format.

27:24	FAM	RO	0x0	Family
				This field provides the family identification of the device within the Stellaris product portfolio. The value is encoded as follows (all other encodings are reserved):

Value Description

0x0 Stellaris family of microcontrollers, that is, all devices with external part numbers starting with LM3S, LM4S, and LM4F.

23:16 PARTNO RO 0xC1 Part Number

This field provides the part number of the device within the family. The reset value shown indicates the LM4F232H5QC microcontroller.

Bit/Field	Name	Туре	Reset	Description
15:13	PINCOUNT	RO	0x2	Package Pin Count
				This field specifies the number of pins on the device package. The value is encoded as follows (all other encodings are reserved):
				Value Description
				0x0 28-pin package
				0x1 48-pin package
				0x2 100-pin package
				0x3 64-pin package
				0x4 144-pin package
				0x5 157-pin package
12:8	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
7:5	TEMP	RO	0x1	Temperature Range
				This field specifies the temperature rating of the device. The value is encoded as follows (all other encodings are reserved):
				Value Description
				0x0 Commercial temperature range (0°C to 70°C)
				0x1 Industrial temperature range (-40°C to 85°C)
				0x2 Extended temperature range (-40°C to 105°C)
4:3	PKG	RO	0x1	Package Type
				This field specifies the package type. The value is encoded as follows (all other encodings are reserved):
				Value Description
				0x0 SOIC package
				0x1 LQFP package
				0x2 BGA package
2	ROHS	RO	0x1	RoHS-Compliance
				This bit specifies whether the device is RoHS-compliant. A 1 indicates the part is RoHS-compliant.
1:0	QUAL	RO	-	Qualification Status
				This field specifies the qualification status of the device. The value is encoded as follows (all other encodings are reserved):
				Value Description
				0x0 Engineering Sample (unqualified)
				0x1 Pilot Production (unqualified)
				0x2 Fully Qualified
				•

Register 3: Brown-Out Reset Control (PBORCTL), offset 0x030

This register is responsible for controlling reset conditions after initial power-on reset.

The BOR voltage values and center points are based on simulation only. These values are yet to be characterized and are subject to change.

Brown-Out Reset Control (PBORCTL)

BOR1

reserved

R/W

RO

0

Base 0x400F.E000 Offset 0x030 Type R/W, reset 0x0000.7FFF

2

,,	,															
	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16
		1	1	1	i .		1		n rad			ı		1		1
								rese	erved •				1			
Type	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO
Reset	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0
	15	14	13	12	11	10	9	8	7	6	5	4	3	2	1	0
		•	1	1	•		reserved					•		BOR0	BOR1	reserved
							10001100							Borto	DOIN	10001100
Type	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	R/W	R/W	RO
Reset	0	0	0	0	0	0	0	0	0	0	0	0	0	1	1	0
Е	3it/Field		Nar	me	Ty	pe	Reset	Des	cription							
	31:3		rese	rved	R	0	0	Soft	ware sho	ould not	relv on t	he value	of a res	erved bit	. To prov	/ide
									patibility							
								0011			o pi ou	,		S. 3001 1		

E	BOR0	R/W	1	VDD under BOR0 Event Action
				The VDD BOR0 trip value is 3.02V +/- 90mv.

Value Description

VDD under BOR1 Event Action

- A BOR0 event causes an interrupt to be generated in the interrupt controller.
 - A BOR0 event causes a reset of the microcontroller.

preserved across a read-modify-write operation.

The VD	DD BOR1 trip value is 2.88V +/- 90mv.
Value	Description
	A BOR1 event causes an interrupt to be generated to the interrupt controller.
1	A BOR1 event causes a reset of the microcontroller.

Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.

This bit is cleared by writing a 1 to the VDDAMIS bit in the MISC register.

compatibility with future products, the value of a reserved bit should be

Software should not rely on the value of a reserved bit. To provide

preserved across a read-modify-write operation.

Register 4: Raw Interrupt Status (RIS), offset 0x050


This register indicates the status for system control raw interrupts. An interrupt is sent to the interrupt controller if the corresponding bit in the **Interrupt Mask Control (IMC)** register is set. Writing a 1 to the corresponding bit in the **Masked Interrupt Status and Clear (MISC)** register clears an interrupt status bit.

Raw Interrupt Status (RIS)

Base 0x400F.E000

9

Offset 0x050 Type RO, reset 0x0000.0000



RO

0

reserved

Bit/Field	Name	Туре	Reset	Description
8	MOSCPUPRIS	RO	0	MOSC Power Up Raw Interrupt Status
				Value Description
				Sufficient time has passed for the MOSC to reach the expected frequency. The value for this power-up time is indicated by T _{MOSC_START} .
				0 Sufficient time has not passed for the MOSC to reach the expected frequency.
				This bit is cleared by writing a 1 to the MOSCPUPMIS bit in the MISC register.
7	USBPLLLRIS	RO	0	USB PLL Lock Raw Interrupt Status
				Value Description
				1 The USB PLL timer has reached T _{READY} indicating that sufficient time has passed for the USB PLL to lock.
				0 The USB PLL timer has not reached T _{READY} .
				This bit is cleared by writing a 1 to the <code>USBPLLLMIS</code> bit in the MISC register.
6	PLLLRIS	RO	0	PLL Lock Raw Interrupt Status
				Value Description
				The PLL timer has reached T _{READY} indicating that sufficient time has passed for the PLL to lock.
				0 The PLL timer has not reached T _{READY} .
				This bit is cleared by writing a 1 to the PLLLMIS bit in the MISC register.
5:4	reserved	RO	0x0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
3	MOFRIS	RO	0	Main Oscillator Failure Raw Interrupt Status
				Value Description
				The MOSCIM bit in the MOSCCTL register is set and the main oscillator has failed.
				0 The main oscillator has not failed.
				This bit is cleared by writing a 1 to the MOFMIS bit in the MISC register.
2	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.

Bit/Field	Name	Туре	Reset	Description
1	BOR1RIS	RO	0	VDD under BOR1 Raw Interrupt Status
				Value Description 1 A VDDS BOR1 condition is currently active. 0 A VDDS BOR1 condition is not currently active.
				Note the BOR1 bit in the PBORCTL register must be cleared to cause an interrupt due to a BOR1 Event. This bit is cleared by writing a 1 to the BOR1MIS bit in the MISC register.
0	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.

February 20, 2013 247


Register 5: Interrupt Mask Control (IMC), offset 0x054

This register contains the mask bits for system control raw interrupts. A raw interrupt, indicated by a bit being set in the **Raw Interrupt Status (RIS)** register, is sent to the interrupt controller if the corresponding bit in this register is set.

Interrupt Mask Control (IMC)

Base 0x400F.E000

Offset 0x054 Type R/W, reset 0x0000.0000



Bit/Field	Name	Туре	Reset	Description
31:12	reserved	RO	0x0000.00	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
11	BOR0IM	R/W	0	VDD under BOR0 Interrupt Mask
				Value Description
				An interrupt is sent to the interrupt controller when the BORORIS bit in the RIS register is set.
				O The BORORIS interrupt is suppressed and not sent to the interrupt controller.
10	VDDAIM	R/W	0	VDDA Power OK Interrupt Mask
				Value Description
				An interrupt is sent to the interrupt controller when the VDDARIS bit in the RIS register is set.
				O The VDDARIS interrupt is suppressed and not sent to the interrupt controller.
9	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
8	MOSCPUPIM	R/W	0	MOSC Power Up Interrupt Mask
				Value Description

Value Description

- 1 An interrupt is sent to the interrupt controller when the MOSCPUPRIS bit in the RIS register is set.
- The MOSCPUPRIS interrupt is suppressed and not sent to the interrupt controller.

Bit/Field	Name	Туре	Reset	Description
7	USBPLLLIM	R/W	0	USB PLL Lock Interrupt Mask
				Value Description
				An interrupt is sent to the interrupt controller when the USBPLLLRIS bit in the RIS register is set.
				O The USBPLLLRIS interrupt is suppressed and not sent to the interrupt controller.
6	PLLLIM	R/W	0	PLL Lock Interrupt Mask
				Value Description
				An interrupt is sent to the interrupt controller when the PLLLRIS bit in the RIS register is set.
				0 The PLLLRIS interrupt is suppressed and not sent to the interrupt controller.
5:4	reserved	RO	0x0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
3	MOFIM	R/W	0	Main Oscillator Failure Interrupt Mask
				Value Description
				An interrupt is sent to the interrupt controller when the MOFRIS bit in the RIS register is set.
				O The MOFRIS interrupt is suppressed and not sent to the interrupt controller.
2	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
1	BOR1IM	R/W	0	VDD under BOR1 Interrupt Mask
				Value Description
				An interrupt is sent to the interrupt controller when the BOR1RIS bit in the RIS register is set.
				O The BOR1RIS interrupt is suppressed and not sent to the interrupt controller.
0	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.

February 20, 2013 249


Register 6: Masked Interrupt Status and Clear (MISC), offset 0x058

On a read, this register gives the current masked status value of the corresponding interrupt in the Raw Interrupt Status (RIS) register. All of the bits are R/W1C, thus writing a 1 to a bit clears the corresponding raw interrupt bit in the RIS register (see page 245).

Masked Interrupt Status and Clear (MISC)

Base 0x400F.E000

Offset 0x058
Type R/W1C, reset 0x0000.0000



Bit/Field	Name	Туре	Reset	Description
31:12	reserved	RO	0x0000.00	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
11	BOR0MIS	R/W1C	0	VDD under BOR0 Masked Interrupt Status
				Value Description
				When read, a 1 indicates that an unmasked interrupt was signaled because of a BOR0 condition.
				Writing a 1 to this bit clears it and also the BORORIS bit in the RIS register.
				When read, a 0 indicates that a BOR0 condition has not occurred.
				A write of 0 has no effect on the state of this bit.
10	VDDAMIS	R/W1C	0	VDDA Power OK Masked Interrupt Status
				Value Description
				When read, a 1 indicates that an unmasked interrupt was signaled because VDDA was below the proper functioning

voltage.

Writing a 1 to this bit clears it and also the $\mathtt{VDDARIS}$ bit in the RIS register.

0 When read, a 0 indicates that VDDA power is good. A write of 0 has no effect on the state of this bit.

9 reserved RO Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.

Bit/Field	Name	Туре	Reset	Description
8	MOSCPUPMIS	R/W1C	0	MOSC Power Up Masked Interrupt Status
				Value Description
				When read, a 1 indicates that an unmasked interrupt was signaled because sufficient time has passed for the MOSC PLL to lock.
				Writing a 1 to this bit clears it and also the MOSCPUPRIS bit in the RIS register.
				0 When read, a 0 indicates that sufficient time has not passed for the MOSC PLL to lock.
				A write of 0 has no effect on the state of this bit.
7	USBPLLLMIS	R/W1C	0	USB PLL Lock Masked Interrupt Status
				Value Description
				When read, a 1 indicates that an unmasked interrupt was signaled because sufficient time has passed for the USB PLL to lock.
				Writing a 1 to this bit clears it and also the <code>USBPLLLRIS</code> bit in the RIS register.
				When read, a 0 indicates that sufficient time has not passed for the USB PLL to lock.
				A write of 0 has no effect on the state of this bit.
6	PLLLMIS	R/W1C	0	PLL Lock Masked Interrupt Status
				Value Description
				When read, a 1 indicates that an unmasked interrupt was signaled because sufficient time has passed for the PLL to lock.
				Writing a 1 to this bit clears it and also the PLLLRIS bit in the RIS register.
				When read, a 0 indicates that sufficient time has not passed for the PLL to lock.
				A write of 0 has no effect on the state of this bit.
5:4	reserved	RO	0x0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
3	MOFMIS	RO	0	Main Oscillator Failure Masked Interrupt Status
				Value Description
				When read, a 1 indicates that an unmasked interrupt was signaled because the main oscillator failed.
				Writing a 1 to this bit clears it and also the MOFRIS bit in the RIS register.
				0 When read, a 0 indicates that the main oscillator has not failed.
				A write of 0 has no effect on the state of this bit.

February 20, 2013 251

Bit/Field	Name	Type	Reset	Description
2	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
1	BOR1MIS	R/W1C	0	VDD under BOR1 Masked Interrupt Status
				Value Description
				When read, a 1 indicates that an unmasked interrupt was signaled because of a BOR1 condition.
				Writing a 1 to this bit clears it and also the BORIRIS bit in the RIS register.
				When read, a 0 indicates that a BOR1 condition has not occurred.
				A write of 0 has no effect on the state of this bit.
0	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.

Register 7: Reset Cause (RESC), offset 0x05C

This register is set with the reset cause after reset. The bits in this register are sticky and maintain their state across multiple reset sequences, except when an power-on reset is the cause, in which case, all bits other than POR in the RESC register are cleared.


Reset Cause (RESC)

Base 0x400F.E000 Offset 0x05C Type R/W, reset -

5

WDT1

R/W



Bit/Field	Name	Type	Reset	Description
31:17	reserved	RO	0x000	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
16	MOSCFAIL	R/W	_	MOSC Failure Reset

Value Description

- When read, this bit indicates that the MOSC circuit was enabled for clock validation and failed while the MOSCIM bit in the MOSCCTL register is clear, generating a reset event.
- 0 When read, this bit indicates that a MOSC failure has not generated a reset since the previous power-on reset. Writing a 0 to this bit clears it.

15:6	reserved	RO	0x00	Software should not rely on the value of a reserved bit. To provide
				compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.

Value Description

Watchdog Timer 1 Reset

- When read, this bit indicates that Watchdog Timer 1 timed out 1 and generated a reset.
- 0 When read, this bit indicates that Watchdog Timer 1 has not generated a reset since the previous power-on reset. Writing a 0 to this bit clears it.

Bit/Field	Name	Туре	Reset	Description
4	SW	R/W	-	Software Reset
				 Value Description 1 When read, this bit indicates that a software reset has caused a reset event. 0 When read, this bit indicates that a software reset has not generated a reset since the previous power-on reset. Writing a 0 to this bit clears it.
3	WDT0	R/W	-	Watchdog Timer 0 Reset Value Description
				When read, this bit indicates that Watchdog Timer 0 timed out and generated a reset.
				When read, this bit indicates that Watchdog Timer 0 has not generated a reset since the previous power-on reset. Writing a 0 to this bit clears it.
2	BOR	R/W	-	Brown-Out Reset
				Value Description
				When read, this bit indicates that a brown-out (BOR0 or BOR1) reset has caused a reset event.
				 When read, this bit indicates that a brown-out (BOR0 or BOR1) reset has not generated a reset since the previous power-on reset. Writing a 0 to this bit clears it.
1	POR	R/W	-	Power-On Reset
				Value Description
				When read, this bit indicates that a power-on reset has caused a reset event.
				When read, this bit indicates that a power-on reset has not generated a reset.
				Writing a 0 to this bit clears it.
0	EXT	R/W	-	External Reset
				Value Description
				When read, this bit indicates that an external reset (RST assertion) has caused a reset event.
				When read, this bit indicates that an external reset (RST assertion) has not caused a reset event since the previous power-on reset.
				Writing a 0 to this bit clears it.

Register 8: Run-Mode Clock Configuration (RCC), offset 0x060

The bits in this register configure the system clock and oscillators.


Important: Write the **RCC** register prior to writing the **RCC2** register. If a subsequent write to the **RCC** register is required, include another register access after writing the **RCC** register and before writing the **RCC2** register.

The USEPWMDIV and PWMDIV fields in the **PWM Peripheral Configuration (PWMPC)** register should be used to control the PWM clock. To support legacy software, the USEPWMDIV and PWMDIV fields in this register are available. A write to these legacy fields also writes the corresponding fields in the **PWMPC** register. If these fields are changed by writing to this register, they can be read back correctly with a read of this register. If software uses the **PWMPC** register to configure the PWM clock, the PWM clock operates as specified, but the value of USEPWMDIV and PWMDIV fields in this register are not modified.

Run-Mode Clock Configuration (RCC)

Base 0x400F.E000 Offset 0x060

Type R/W, reset 0x078E.3AD1



Bit/Field	Name	Type	Reset	Description
31:28	reserved	RO	0x0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
27	ACG	R/W	0	Auto Clock Gating

This bit specifies whether the system uses the Sleep-Mode Clock Gating Control (SCGCn) registers and Deep-Sleep-Mode Clock Gating Control (DCGCn) registers if the microcontroller enters a Sleep or Deep-Sleep mode (respectively).

Value Description

- The SCGCn or DCGCn registers are used to control the clocks distributed to the peripherals when the microcontroller is in a sleep mode. The SCGCn and DCGCn registers allow unused peripherals to consume less power when the microcontroller is in a sleep mode.
- The Run-Mode Clock Gating Control (RCGCn) registers are used when the microcontroller enters a sleep mode.

The **RCGCn** registers are always used to control the clocks in Run mode.

Bit/Field	Name	Туре	Reset	Description
26:23	SYSDIV	R/W	0xF	System Clock Divisor
				Specifies which divisor is used to generate the system clock from either the PLL output or the oscillator source (depending on how the BYPASS bit in this register is configured). See Table 5-4 on page 227 for bit encodings.
				If the SYSDIV value is less than MINSYSDIV (see page 420), and the PLL is being used, then the MINSYSDIV value is used as the divisor.
				If the PLL is not being used, the SYSDIV value can be less than MINSYSDIV.
22	USESYSDIV	R/W	0	Enable System Clock Divider
				Value Description
				The system clock divider is the source for the system clock. The system clock divider is forced to be used when the PLL is selected as the source.
				If the USERCC2 bit in the RCC2 register is set, then the SYSDIV2 field in the RCC2 register is used as the system clock divider rather than the SYSDIV field in this register.
				0 The system clock is used undivided.
21	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
20	USEPWMDIV	R/W	0	Enable PWM Clock Divisor
				Value Description
				1 The PWM clock divider is the source for the PWM clock.
				0 The system clock is the source for the PWM clock.
				Note that when the PWM divisor is used, it is applied to the clock for both PWM modules.
19:17	PWMDIV	R/W	0x7	PWM Unit Clock Divisor
				This field specifies the binary divisor used to predivide the system clock down for use as the timing reference for the PWM module. The rising edge of this clock is synchronous with the system clock.
				Value Divisor
				0x0 /2
				0x1 /4
				0x2 /8
				0x3 /16
				0x4 /32
				0x5 /64
				0x6 /64
				0x7 /64 (default)

Bit/Field	Name	Туре	Reset	Description
16:14	reserved	RO	0x0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
13	PWRDN	R/W	1	PLL Power Down
				Value Description
				1 The PLL is powered down. Care must be taken to ensure that another clock source is functioning and that the BYPASS bit is set before setting this bit.
				0 The PLL is operating normally.
12	reserved	RO	1	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
11	BYPASS	R/W	1	PLL Bypass
				Value Description
				4. The contains also less destroy of fears the COO services and divided

- The system clock is derived from the OSC source and divided by the divisor specified by SYSDIV.
- O The system clock is the PLL output clock divided by the divisor specified by SYSDIV.

See Table 5-4 on page 227 for programming guidelines.

Note: The ADC must be clocked from the PLL or directly from a 16-MHz clock source to operate properly.

Bit/Field	Name	Type	Reset	Description
10:6	XTAI	R/W	0x0B	Crystal Value

This field specifies the crystal value attached to the main oscillator. The encoding for this field is provided below.

Frequencies that may be used with the USB interface are indicated in the table. To function within the clocking requirements of the USB specification, a crystal of 5, 6, 8, 10, 12, or 16 MHz must be used.

Value	Crystal Frequency (MHz) Not Using the PLL	Crystal Frequency (MHz) Using the PLL
0x00-0x5	reser	ved
0x06	4 MHz	reserved
0x07	4.096 MHz	reserved
80x0	4.9152 MHz	reserved
0x09	5 MHz	(USB)
0x0A	5.12 [MHz
0x0B	6 MHz	(USB)
0x0C	6.144	MHz
0x0D	7.3728	3 MHz
0x0E	8 MHz	(USB)
0x0F	8.192	MHz
0x10	10.0 MH	z (USB)
0x11	12.0 MH	z (USB)
0x12	12.288	3 MHz
0x13	13.56	MHz
0x14	14.3181	8 MHz
0x15	16.0 MH	z (USB)
0x16	16.384	MHz
0x17	18.0 MH	z (USB)
0x18	20.0 MH	z (USB)
0x19	24.0 MH	z (USB)
0x1A	25.0 MH	z (USB)

Bit/Field	Name	Туре	Reset	Description
5:4	OSCSRC	R/W	0x1	Oscillator Source
				Selects the input source for the OSC. The values are:
				Value Input Source
				0x0 MOSC
				Main oscillator
				0x1 PIOSC
				Precision internal oscillator
				(default)
				0x2 PIOSC/4
				Precision internal oscillator / 4
				0x3 LFIOSC
				Low-frequency internal oscillator
				For additional oscillator sources, see the RCC2 register.
3:1	reserved	RO	0x0	Software should not rely on the value of a reserved bit. To provide
				compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
				preserved doross a read modify write operation.
0	MOSCDIS	R/W	1	Main Oscillator Disable
				Value Description
				1 The main oscillator is disabled (default).
				0 The main oscillator is enabled.

Register 9: GPIO High-Performance Bus Control (GPIOHBCTL), offset 0x06C


This register controls which internal bus is used to access each GPIO port. When a bit is clear, the corresponding GPIO port is accessed across the legacy Advanced Peripheral Bus (APB) bus and through the APB memory aperture. When a bit is set, the corresponding port is accessed across the Advanced High-Performance Bus (AHB) bus and through the AHB memory aperture. Each GPIO port can be individually configured to use AHB or APB, but may be accessed only through one aperture. The AHB bus provides better back-to-back access performance than the APB bus. The address aperture in the memory map changes for the ports that are enabled for AHB access (see Table 10-6 on page 657).

Important: Ports K-N and P-Q are only available on the AHB bus, and therefore the corresponding bits reset to 1. If one of these bits is cleared, the corresponding port is disabled. If any of these ports is in use, read-modify-write operations should be used to change the value of this register so that these ports remain enabled.

GPIO High-Performance Bus Control (GPIOHBCTL)

Base 0x400F.E000 Offset 0x06C

Type R/W, reset 0x0000.7E00



Bit/Field	Name	Type	Reset	Description
31:10	reserved	RO	0x0000.0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
9	PORTK	R/W	1	Port K Advanced High-Performance Bus This bit defines the memory aperture for Port K. Value Description 1 Advanced High-Performance Bus (AHB) 0 Port K is disabled.
8	PORTJ	R/W	0	Port J Advanced High-Performance Bus This bit defines the memory aperture for Port J.

- 1 Advanced High-Performance Bus (AHB)
- 0 Advanced Peripheral Bus (APB). This bus is the legacy bus.

7 PORTH R/W 0 Port H Advanced High-Performance Bus This bit defines the memory aperture for Port H. Value Description 1 Advanced High-Performance Bus (AHB) 0 Advanced Peripheral Bus (APB). This bus is the legacy of the port of the po	bus.
1 Advanced High-Performance Bus (AHB) 0 Advanced Peripheral Bus (APB). This bus is the legacy	bus.
0 Advanced Peripheral Bus (APB). This bus is the legacy	bus.
	bus.
6 PORTG R/W 0 Port G Advanced High-Performance Bus	
This bit defines the memory aperture for Port G.	
Value Description	
1 Advanced High-Performance Bus (AHB)	
0 Advanced Peripheral Bus (APB). This bus is the legacy	bus.
5 PORTF R/W 0 Port F Advanced High-Performance Bus	
This bit defines the memory aperture for Port F.	
Value Description	
1 Advanced High-Performance Bus (AHB)	
0 Advanced Peripheral Bus (APB). This bus is the legacy	bus.
4 PORTE R/W 0 Port E Advanced High-Performance Bus	
This bit defines the memory aperture for Port E.	
Value Description	
1 Advanced High-Performance Bus (AHB)	
0 Advanced Peripheral Bus (APB). This bus is the legacy	bus.
3 PORTD R/W 0 Port D Advanced High-Performance Bus	
This bit defines the memory aperture for Port D.	
Value Description	
1 Advanced High-Performance Bus (AHB)	
0 Advanced Peripheral Bus (APB). This bus is the legacy	bus.
2 PORTC R/W 0 Port C Advanced High-Performance Bus	
This bit defines the memory aperture for Port C.	
Value Description	
1 Advanced High-Performance Bus (AHB)	
0 Advanced Peripheral Bus (APB). This bus is the legacy	bus.

February 20, 2013 261

Bit/Field	Name	Туре	Reset	Description
1	PORTB	R/W	0	Port B Advanced High-Performance Bus This bit defines the memory aperture for Port B.
				Value Description Advanced High-Performance Bus (AHB) Advanced Peripheral Bus (APB). This bus is the legacy bus.
0	PORTA	R/W	0	Port A Advanced High-Performance Bus This bit defines the memory aperture for Port A. Value Description Advanced High-Performance Bus (AHB) Advanced Peripheral Bus (APB). This bus is the legacy bus.

Register 10: Run-Mode Clock Configuration 2 (RCC2), offset 0x070

This register overrides the RCC equivalent register fields, as shown in Table 5-8, when the USERCC2 bit is set, allowing the extended capabilities of the RCC2 register to be used while also providing a means to be backward-compatible to previous parts. Each RCC2 field that supersedes an RCC field is located at the same LSB bit position; however, some RCC2 fields are larger than the corresponding RCC field.

Table 5-8. RCC2 Fields that Override RCC Fields


RCC2 Field	Overrides RCC Field
SYSDIV2, bits[28:23]	SYSDIV, bits[26:23]
PWRDN2, bit[13]	PWRDN, bit[13]
BYPASS2, bit[11]	BYPASS, bit[11]
OSCSRC2, bits[6:4]	OSCSRC, bits[5:4]

Important: Write the **RCC** register prior to writing the **RCC2** register. If a subsequent write to the **RCC** register is required, include another register access after writing the **RCC** register and before writing the **RCC2** register.

Run-Mode Clock Configuration 2 (RCC2)

Base 0x400F.E000 Offset 0x070

Type R/W, reset 0x07C0.6810



Bit/Field	Name	Туре	Reset	Description	
31	USERCC2	R/W	0	Use RCC2	
				Value Description	
				1 The RCC2 register fields override the RCC register fields.	
				The RCC register fields are used, and the fields in RCC2 are ignored.	

30 DIV400 R/W 0 Divide PLL as 400 MHz vs. 200 MHz

This bit, along with the ${\tt SYSDIV2LSB}$ bit, allows additional frequency choices.

- 1 Append the SYSDIV2LSB bit to the SYSDIV2 field to create a 7 bit divisor using the 400 MHz PLL output, see Table 5-6 on page 228.
- 0 Use SYSDIV2 as is and apply to 200 MHz predivided PLL output. See Table 5-5 on page 227 for programming guidelines.

Bit/Field	Name	Туре	Reset	Description
29	reserved	RO	0x0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
28:23	SYSDIV2	R/W	0x0F	System Clock Divisor 2 Specifies which divisor is used to generate the system clock from either the PLL output or the oscillator source (depending on how the BYPASS2 bit is configured). SYSDIV2 is used for the divisor when both the USESYSDIV bit in the RCC register and the USERCC2 bit in this register are set. See Table 5-5 on page 227 for programming guidelines.
22	SYSDIV2LSB	R/W	1	Additional LSB for SYSDIV2 When DIV400 is set, this bit becomes the LSB of SYSDIV2. If DIV400 is clear, this bit is not used. See Table 5-5 on page 227 for programming guidelines. This bit can only be set or cleared when DIV400 is set.
21:15	reserved	RO	0x0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
14	USBPWRDN	R/W	1	Power-Down USB PLL Value Description 1 The USB PLL is powered down. 0 The USB PLL operates normally.
13	PWRDN2	R/W	1	Power-Down PLL 2 Value Description 1 The PLL is powered down. 0 The PLL operates normally.
12	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
11	BYPASS2	R/W	1	PLL Bypass 2 Value Description 1 The system clock is derived from the OSC source and divided by the divisor specified by SYSDIV2. 0 The system clock is the PLL output clock divided by the divisor specified by SYSDIV2. See Table 5-5 on page 227 for programming guidelines. Note: The ADC must be clocked from the PLL or directly from a 16-MHz clock source to operate properly.
10:7	reserved	RO	0x0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.

Bit/Field	Name	Туре	Reset	Description
6:4	OSCSRC2	R/W	0x1	Oscillator Source 2 Selects the input source for the OSC. The values are:
				Value Description
				0x0 MOSC
				Main oscillator
				0x1 PIOSC
				Precision internal oscillator
				0x2 PIOSC/4
				Precision internal oscillator / 4
				0x3 LFIOSC
				Low-frequency internal oscillator
				0x4-0x6 Reserved
				0x7 32.768 kHz
				32.768-kHz external oscillator
3:0	reserved	RO	0x0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.


Register 11: Main Oscillator Control (MOSCCTL), offset 0x07C

This register provides control over the features of the main oscillator, including the ability to enable the MOSC clock verification circuit, what action to take when the MOSC fails, and whether or not a crystal is connected. When enabled, this circuit monitors the frequency of the MOSC to verify that the oscillator is operating within specified limits. If the clock goes invalid after being enabled, the microcontroller issues a power-on reset and reboots to the NMI handler or generates an interrupt.

Main Oscillator Control (MOSCCTL)

Base 0x400F.E000 Offset 0x07C

Type R/W, reset 0x0000.0000



- 1 The MOSC monitor circuit is enabled.
- 0 The MOSC monitor circuit is disabled.


Register 12: Deep Sleep Clock Configuration (DSLPCLKCFG), offset 0x144

This register provides configuration information for the hardware control of Deep Sleep Mode.

Deep Sleep Clock Configuration (DSLPCLKCFG)

Base 0x400F.E000 Offset 0x144

Type R/W, reset 0x0780.0000



Bit/Field	Name	Type	Reset	Description
31:29	reserved	RO	0x0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.

28:23 DSDIVORIDE R/W 0x0F Divider Field Override

If Deep-Sleep mode is enabled when the PLL is running, the PLL is disabled. This 6-bit field contains a system divider field that overrides the SYSDIV field in the RCC register or the SYSDIV2 field in the RCC2 register during Deep Sleep. This divider is applied to the source selected by the DSOSCSRC field.

 Value
 Description

 0x0
 /1

 0x1
 /2

 0x2
 /3

 0x3
 /4

 ...
 0x3F

 /64

22:7 reserved RO 0x000 Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.


Bit/Field	Name	Туре	Reset	Description
6:4	DSOSCSRC	R/W	0x0	Clock Source Specifies the clock source during Deep-Sleep mode.
				Value Description
				0x0 MOSC
				Use the main oscillator as the source. To use the MOSC as the Deep-Sleep mode clock source, the MOSC must also be configured as the Run mode clock source in the Run-Mode Clock Configuration (RCC) register.
				Note: If the PIOSC is being used as the clock reference for the PLL, the PIOSC is the clock source instead of MOSC in Deep-Sleep mode.
				0x1 PIOSC
				Use the precision internal 16-MHz oscillator as the source.
				0x2 Reserved
				0x3 LFIOSC
				Use the low-frequency internal oscillator as the source.
				0x4-0x6 Reserved
				0x7 32.768 kHz
				Use the Hibernation module 32.768-kHz external oscillator as the source.
3:0	reserved	RO	0x0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.

Register 13: System Properties (SYSPROP), offset 0x14C

This register provides information on whether certain System Control properties are present on the microcontroller.

System Properties (SYSPROP)

Base 0x400F.E000 Offset 0x14C Type RO, reset 0x0000.1D31



Bit/Field	Name	Type	Reset	Description
31:1	reserved	RO	0xE98	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
0	FPU	RO	0x1	FPU Present

This bit indicates if the FPU is present in the Cortex-M4 core.

Value Description

0 FPU is not present.

FPU is present.


Register 14: Precision Internal Oscillator Calibration (PIOSCCAL), offset 0x150

This register provides the ability to update or recalibrate the precision internal oscillator. Note that a 32.768-kHz oscillator must be used as the Hibernation module clock source for the user to be able to calibrate the PIOSC.

Precision Internal Oscillator Calibration (PIOSCCAL)

Base 0x400F.E000 Offset 0x150

Type R/W, reset 0x0000.0000



Bit/Field	Name	Туре	Reset	Description
6:0	UT	R/W	0x0	User Trim Value User trim value that can be loaded into the PIOSC. Refer to "Main PLL Frequency Configuration" on page 229 for more information on calibrating the PIOSC.


February 20, 2013 271

Register 15: Precision Internal Oscillator Statistics (PIOSCSTAT), offset 0x154

This register provides the user information on the PIOSC calibration. Note that a 32.768-kHz oscillator must be used as the Hibernation module clock source for the user to be able to calibrate the PIOSC.

Precision Internal Oscillator Statistics (PIOSCSTAT)

Base 0x400F.E000 Offset 0x154 Type RO, reset 0x0000.0040



Bit/Field	Name	Type	Reset	Description
31:23	reserved	RO	0x00	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
22:16	DT	RO	-	Default Trim Value
				This field contains the default trim value. This value is loaded into the PIOSC after every full power-up.
15:10	reserved	RO	0x0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
9:8	RESULT	RO	0	Calibration Result
				Value Description
				0x0 Calibration has not been attempted.
				0x1 The last calibration operation completed to meet 1% accuracy.
				0x2 The last calibration operation failed to meet 1% accuracy.
				0x3 Reserved
7	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
6:0	СТ	RO	0x40	Calibration Trim Value
				This field contains the trips value from the least selibration are estimated.

This field contains the trim value from the last calibration operation. After factory calibration \mathtt{CT} and \mathtt{DT} are the same.

Register 16: PLL Frequency 0 (PLLFREQ0), offset 0x160

This register always contains the current M value presented to the system PLL.

The PLL frequency can be calculated using the following equation:

PLL frequency = (XTAL frequency * MDIV) /
$$((Q + 1) * (N + 1))$$
 where


MDIV = MINT + (MFRAC / 1024)

The Q and N values are shown in the PLLFREQ1 register. Table 24-14 on page 1391 shows the M, Q, and N values as well as the resulting PLL frequency for the various XTAL configurations.

PLL Frequency 0 (PLLFREQ0)

Base 0x400F.E000

Offset 0x160 Type RO, reset 0x0000.0032



Bit/Field	Name	Type	Reset	Description
31:20	reserved	RO	0x000	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
19:10	MFRAC	RO	0x32	PLL M Fractional Value This field contains the integer value of the PLL M value.
9:0	MINT	RO	0x00	PLL M Integer Value This field contains the integer value of the PLL M value


Register 17: PLL Frequency 1 (PLLFREQ1), offset 0x164

This register always contains the current Q and N values presented to the system PLL.

The M value is shown in the PLLFREQ0 register. Table 24-14 on page 1391 shows the M, Q, and N values as well as the resulting PLL frequency for the various XTAL configurations.

PLL Frequency 1 (PLLFREQ1)

Base 0x400F.E000 Offset 0x164 Type RO, reset 0x0000.0001



Bit/Field	Name	Type	Reset	Description
31:13	reserved	RO	0x0000.0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
12:8	Q	RO	0x0	PLL Q Value This field contains the PLL Q value.
7:5	reserved	RO	0x0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
4:0	N	RO	0x1	PLL N Value This field contains the PLL N value.


Register 18: PLL Status (PLLSTAT), offset 0x168

This register shows the direct status of the PLL lock.

PLL Status (PLLSTAT)

Base 0x400F.E000 Offset 0x168

Type RO, reset 0x0000.0000



Bit/Field	Name	Туре	Reset	Description
31:1	reserved	RO	0x0000.000	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
0	LOCK	RO	0x0	PLL Lock

- 1 The PLL powered and locked.
- 0 The PLL is unpowered or is not yet locked.


Register 19: Watchdog Timer Peripheral Present (PPWD), offset 0x300

The **PPWD** register provides software information regarding the watchdog modules.

Important: This register should be used to determine which watchdog timers are implemented on this microcontroller. However, to support legacy software, the DC1 register is available. A read of the **DC1** register correctly identifies if a legacy module is present.

Watchdog Timer Peripheral Present (PPWD)

Base 0x400F.E000 Offset 0x300 Type RO, reset 0x0000.0003



Bit/Field	Name	Туре	Reset	Description
31:2	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
1	P1	RO	0x1	Watchdog Timer 1 Present
				Value Description
				1 Watchdog module 1 is present.
				0 Watchdog module 1 is not present.
0	P0	RO	0x1	Watchdog Timer 0 Present
				Value Description

- 1 Watchdog module 0 is present.
- 0 Watchdog module 0 is not present.

Register 20: 16/32-Bit General-Purpose Timer Peripheral Present (PPTIMER), offset 0x304


The **PPTIMER** register provides software information regarding the 16/32-bit general-purpose timer modules.

Important: This register should be used to determine which timers are implemented on this microcontroller. However, to support legacy software, the DC2 register is available. A read of the DC2 register correctly identifies if a legacy module is present. Software must use this register to determine if a module that is not supported by the DC2 register is present.

16/32-Bit General-Purpose Timer Peripheral Present (PPTIMER)

Base 0x400F.E000

Offset 0x304 Type RO, reset 0x0000.003F



Bit/Field	Name	Туре	Reset	Description
31:6	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
5	P5	RO	0x1	 16/32-Bit General-Purpose Timer 5 Present Value Description 16/32-bit general-purpose timer module 5 is present. 16/32-bit general-purpose timer module 6 is not present.
4	P4	RO	0x1	 16/32-Bit General-Purpose Timer 4 Present Value Description 1 16/32-bit general-purpose timer module 4 is present. 0 16/32-bit general-purpose timer module 4 is not present.
3	P3	RO	0x1	16/32-Bit General-Purpose Timer 3 Present Value Description

1

0

16/32-bit general-purpose timer module 3 is present.

16/32-bit general-purpose timer module 3 is not present.

Bit/Field	Name	Туре	Reset	Description
2	P2	RO	0x1	16/32-Bit General-Purpose Timer 2 Present
				Value Description 1 16/32-bit general-purpose timer module 2 is present. 0 16/32-bit general-purpose timer module 2 is not present.
1	P1	RO	0x1	16/32-Bit General-Purpose Timer 1 Present
				Value Description
				1 16/32-bit general-purpose timer module 1 is present.
				0 16/32-bit general-purpose timer module 1 is not present.
0	P0	RO	0x1	16/32-Bit General-Purpose Timer 0 Present
				Value Description
				1 16/32-bit general-purpose timer module 0 is present.
				0 16/32-bit general-purpose timer module 0 is not present.

Register 21: General-Purpose Input/Output Peripheral Present (PPGPIO), offset 0x308


The **PPGPIO** register provides software information regarding the general-purpose input/output modules.

Important: This register should be used to determine which GPIO ports are implemented on this microcontroller. However, to support legacy software, the DC4 register is available. A read of the DC4 register correctly identifies if a legacy module is present. Software must use this register to determine if a module that is not supported by the DC4 register is present.

General-Purpose Input/Output Peripheral Present (PPGPIO)

Base 0x400F.E000

Offset 0x308 Type RO, reset 0x0000.03FF



Bit/Field	Name	Type	Reset	Description
31:15	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
14	P14	RO	0x0	GPIO Port Q Present
				Value Description
				1 GPIO Port Q is present.
				0 GPIO Port Q is not present.
13	P13	RO	0x0	GPIO Port P Present
				Value Description
				1 GPIO Port P is present.
				0 GPIO Port P is not present.
12	P12	RO	0x0	GPIO Port N Present
				Value Description
				1 GPIO Port N is present.

0

GPIO Port N is not present.

Bit/Field	Name	Туре	Reset	Description
11	P11	RO	0x0	GPIO Port M Present
				Value Description 1 GPIO Port M is present. 0 GPIO Port M is not present.
10	P10	RO	0x0	GPIO Port L Present
				Value Description 1 GPIO Port L is present. 0 GPIO Port L is not present.
9	P9	RO	0x1	GPIO Port K Present
				Value Description 1 GPIO Port K is present. 0 GPIO Port K is not present.
8	P8	RO	0x1	GPIO Port J Present
				Value Description GPIO Port J is present. GPIO Port J is not present.
7	P7	RO	0x1	GPIO Port H Present
				Value Description 1 GPIO Port H is present. 0 GPIO Port H is not present.
6	P6	RO	0x1	GPIO Port G Present
				Value Description 1 GPIO Port G is present. 0 GPIO Port G is not present.
5	P5	RO	0x1	GPIO Port F Present
				Value Description 1 GPIO Port F is present. 0 GPIO Port F is not present.

Bit/Field	Name	Туре	Reset	Description
4	P4	RO	0x1	GPIO Port E Present
				Value Description 1 GPIO Port E is present. 0 GPIO Port E is not present.
3	P3	RO	0x1	GPIO Port D Present
				Value Description 1 GPIO Port D is present. 0 GPIO Port D is not present.
2	P2	RO	0x1	GPIO Port C Present
				Value Description 1 GPIO Port C is present. 0 GPIO Port C is not present.
1	P1	RO	0x1	GPIO Port B Present
				Value Description GPIO Port B is present. GPIO Port B is not present.
0	P0	RO	0x1	GPIO Port A Present
				Value Description 1 GPIO Port A is present. 0 GPIO Port A is not present.

February 20, 2013 281

Register 22: Micro Direct Memory Access Peripheral Present (PPDMA), offset 0x30C


The **PPDMA** register provides software information regarding the µDMA module.

Important: This register should be used to determine if the μDMA module is implemented on this microcontroller. However, to support legacy software, the **DC7** register is available. A read of the **DC7** register correctly identifies if the μDMA module is present.

Micro Direct Memory Access Peripheral Present (PPDMA)

Base 0x400F.E000 Offset 0x30C

Type RO, reset 0x0000.0001



Bit/Field	Name	Туре	Reset	Description
31:1	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
0	P0	RO	0x1	μDMA Module Present

Value Description

1 μDMA module is present.

0 μ DMA module is not present.


Register 23: Hibernation Peripheral Present (PPHIB), offset 0x314

The PPHIB register provides software information regarding the Hibernation module.

Important: This register should be used to determine if the Hibernation module is implemented on this microcontroller. However, to support legacy software, the DC1 register is available. A read of the **DC1** register correctly identifies if the Hibernation module is present.

Hibernation Peripheral Present (PPHIB)

Base 0x400F.E000 Offset 0x314 Type RO, reset 0x0000.0001



Bit/Field	Name	Type	Reset	Description
31:1	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
0	P0	RO	0x1	Hibernation Module Present

- 1 Hibernation module is present.
- Hibernation module is not present. 0

Register 24: Universal Asynchronous Receiver/Transmitter Peripheral Present (PPUART), offset 0x318


The **PPUART** register provides software information regarding the UART modules.

Important: This register should be used to determine which UART modules are implemented on this microcontroller. However, to support legacy software, the DC2 register is available. A read of the **DC2** register correctly identifies if a legacy UART module is present. Software must use this register to determine if a module that is not supported by the **DC2** register is present.

Universal Asynchronous Receiver/Transmitter Peripheral Present (PPUART)

Base 0x400F.E000

Offset 0x318
Type RO, reset 0x0000.00FF



Bit/Field	Name	Туре	Reset	Description
31:8	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
7	P7	RO	0x1	UART Module 7 Present
				Value Description
				1 UART module 7 is present.
				0 UART module 7 is not present.
6	P6	RO	0x1	UART Module 6 Present
				Value Description
				1 UART module 6 is present.
				0 UART module 6 is not present.
5	P5	RO	0x1	UART Module 5 Present
				Value Description
				1 UART module 5 is present.

0

UART module 5 is not present.

Bit/Field	Name	Туре	Reset	Description
4	P4	RO	0x1	UART Module 4 Present
				Value Description 1 UART module 4 is present. 0 UART module 4 is not present.
3	P3	RO	0x1	UART Module 3 Present
				Value Description
				1 UART module 3 is present.
				0 UART module 3 is not present.
2	P2	RO	0x1	UART Module 2 Present
				Value Description
				1 UART module 2 is present.
				0 UART module 2 is not present.
1	P1	RO	0x1	UART Module 1 Present
				Value Description
				1 UART module 1 is present.
				0 UART module 1 is not present.
0	P0	RO	0x1	UART Module 0 Present
				Value Description
				1 UART module 0 is present.
				0 UART module 0 is not present.

February 20, 2013 285

Register 25: Synchronous Serial Interface Peripheral Present (PPSSI), offset 0x31C


The **PPSSI** register provides software information regarding the SSI modules.

Important: This register should be used to determine which SSI modules are implemented on this microcontroller. However, to support legacy software, the DC2 register is available. A read of the DC2 register correctly identifies if a legacy SSI module is present. Software must use this register to determine if a module that is not supported by the DC2 register is present.

Synchronous Serial Interface Peripheral Present (PPSSI)

Base 0x400F.E000

Offset 0x31C Type RO, reset 0x0000.000F



Bit/Field	Name	Туре	Reset	Description
31:4	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
3	P3	RO	0x1	SSI Module 3 Present
				Value Description
				1 SSI module 3 is present.
				0 SSI module 3 is not present.
2	P2	RO	0x1	SSI Module 2 Present
				Value Description
				1 SSI module 2 is present.
				0 SSI module 2 is not present.
1	P1	RO	0x1	SSI Module 1 Present
				Value Description
				1 SSI module 1 is present.

0

SSI module 1 is not present.

Bit/Field	Name	Туре	Reset	Description
0	P0	RO	0x1	SSI Module 0 Present
				Value Description 1 SSI module 0 is present. 0 SSI module 0 is not present.

February 20, 2013 287

Register 26: Inter-Integrated Circuit Peripheral Present (PPI2C), offset 0x320


The **PPI2C** register provides software information regarding the I²C modules.

Important: This register should be used to determine which I²C modules are implemented on this microcontroller. However, to support legacy software, the **DC2** register is available. A read of the **DC2** register correctly identifies if a legacy I²C module is present. Software must use this register to determine if a module that is not supported by the **DC2** register is present.

Inter-Integrated Circuit Peripheral Present (PPI2C)

Base 0x400F.E000 Offset 0x320

Type RO, reset 0x0000.003F



Bit/Field	Name	Туре	Reset	Description
31:6	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
5	P5	RO	0x1	I ² C Module 5 Present
				Value Description
				1 I ² C module 5 is present.
				0 I ² C module 5 is not present.
4	P4	RO	0x1	I ² C Module 4 Present
				Value Description
				1 I ² C module 4 is present.
				0 I ² C module 4 is not present.
3	P3	RO	0x1	I ² C Module 3 Present
				Value Description
				1 I ² C module 3 is present.
				0 I ² C module 3 is not present.

Bit/Field	Name	Туре	Reset	Description
2	P2	RO	0x1	I ² C Module 2 Present
				Value Description 1 I ² C module 2 is present. 0 I ² C module 2 is not present.
1	P1	RO	0x1	I ² C Module 1 Present
				Value Description 1 I ² C module 1 is present. 0 I ² C module 1 is not present.
0	P0	RO	0x1	I ² C Module 0 Present
				Value Description 1 I ² C module 0 is present. 0 I ² C module 0 is not present.


Register 27: Universal Serial Bus Peripheral Present (PPUSB), offset 0x328

The **PPUSB** register provides software information regarding the USB module.

Important: This register should be used to determine if the USB module is implemented on this microcontroller. However, to support legacy software, the DC6 register is available. A read of the DC6 register correctly identifies if the USB module is present.

Universal Serial Bus Peripheral Present (PPUSB)

Base 0x400F.E000 Offset 0x328 Type RO, reset 0x0000.0001



Bit/Field	Name	Type	Reset	Description
31:1	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
0	P0	RO	0x1	USB Module Present

Value Description

1 USB module is present.

USB module is not present. 0


Register 28: Controller Area Network Peripheral Present (PPCAN), offset 0x334

The **PPCAN** register provides software information regarding the CAN modules.

Important: This register should be used to determine which CAN modules are implemented on this microcontroller. However, to support legacy software, the DC1 register is available. A read of the **DC1** register correctly identifies if a legacy CAN module is present.

Controller Area Network Peripheral Present (PPCAN)

Base 0x400F.E000 Offset 0x334 Type RO, reset 0x0000.0003



Bit/Field	Name	Туре	Reset	Description		
31:2	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.		
1	P1	RO	0x1	CAN Module 1 Present		
				Value Description		
				1 CAN module 1 is present.		
				0 CAN module 1 is not present.		
0	P0	RO	0x1	CAN Module 0 Present		
				Value Description		

Value Description

CAN module 0 is present. 1

0 CAN module 0 is not present.

Register 29: Analog-to-Digital Converter Peripheral Present (PPADC), offset 0x338


The **PPADC** register provides software information regarding the ADC modules.

Important: This register should be used to determine which ADC modules are implemented on this microcontroller. However, to support legacy software, the **DC1** register is available. A read of the **DC1** register correctly identifies if a legacy ADC module is present.

Analog-to-Digital Converter Peripheral Present (PPADC)

Base 0x400F.E000 Offset 0x338

Type RO, reset 0x0000.0003



Bit/Field	Name	Type	Reset	Description		
31:2	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.		
1	P1	RO	0x1	ADC Module 1 Present		
				Value Description 1 ADC module 1 is present. 0 ADC module 1 is not present.		
0	P0	RO	0x1	ADC Module 0 Present		

- 1 ADC module 0 is present.
- 0 ADC module 0 is not present.

Register 30: Analog Comparator Peripheral Present (PPACMP), offset 0x33C

The **PPACMP** register provides software information regarding the analog comparator module.


Important: This register should be used to determine if the analog comparator module is implemented on this microcontroller. However, to support legacy software, the DC2 register is available. A read of the DC2 register correctly identifies if the analog comparator module is present.

Note that the **Analog Comparator Peripheral Properties (ACMPPP)** register indicates how many analog comparator blocks are included in the module.

Analog Comparator Peripheral Present (PPACMP)

Base 0x400F.E000 Offset 0x33C

Type RO, reset 0x0000.0001



Bit/Field	Name	Туре	Reset	Description
31:1	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
0	P0	RO	0x1	Analog Comparator Module Present

- Analog comparator module is present.
- 0 Analog comparator module is not present.


Register 31: Pulse Width Modulator Peripheral Present (PPPWM), offset 0x340

The **PPPWM** register provides software information regarding the PWM modules.

Important: This register should be used to determine which PWM modules are implemented on this microcontroller. However, to support legacy software, the **DC1** register is available. A read of the **DC1** register correctly identifies if the legacy PWM module is present. Software must use this register to determine if a module that is not supported by the **DC1** register is present.

Pulse Width Modulator Peripheral Present (PPPWM)

Base 0x400F.E000 Offset 0x340 Type RO, reset 0x0000.0003



Bit/Field	Name	Type	Reset	Description		
31:2	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.		
1	P1	RO	0x1	PWM Module 1 Present Value Description		
				PWM module 1 is present.		
				0 PWM module 1 is not present.		
0	P0	RO	0x1	PWM Module 0 Present		

- 1 PWM module 0 is present.
- 0 PWM module 0 is not present.

Register 32: Quadrature Encoder Interface Peripheral Present (PPQEI), offset 0x344


The **PPQEI** register provides software information regarding the QEI modules.

Important: This register should be used to determine which QEI modules are implemented on this microcontroller. However, to support legacy software, the **DC2** register is available. A read of the **DC2** register correctly identifies if a legacy QEI module is present.

Quadrature Encoder Interface Peripheral Present (PPQEI)

Base 0x400F.E000 Offset 0x344

Type RO, reset 0x0000.0003



Bit/Field	Name	Type	Reset	Description
31:2	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
1	P1	RO	0x1	QEI Module 1 Present
				Value Description 1 QEI module 1 is present.
				0 QEI module 1 is not present.
0	Р0	RO	0x1	QEI Module 0 Present

- 1 QEI module 0 is present.
- 0 QEI module 0 is not present.


Register 33: EEPROM Peripheral Present (PPEEPROM), offset 0x358

The **PPEEPROM** register provides software information regarding the EEPROM module.

EEPROM Peripheral Present (PPEEPROM)

Base 0x400F.E000 Offset 0x358

Type RO, reset 0x0000.0001



Bit/Field	Name	Туре	Reset	Description
31:1	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
0	P0	RO	0x1	EEPROM Module Present

Value Description

1 EEPROM module is present.

0 EEPROM module is not present.

Register 34: 32/64-Bit Wide General-Purpose Timer Peripheral Present (PPWTIMER), offset 0x35C

The **PPWTIMER** register provides software information regarding the 32/64-bit wide general-purpose timer modules.

32/64-Bit Wide General-Purpose Timer Peripheral Present (PPWTIMER)

Base 0x400F.E000

Offset 0x35C Type RO, reset 0x0000.003F

,,	,															
	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16
	'		ı	•		1	' '	rese	rved		1	•			ı	
Туре	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO
Reset	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0
ı	15	14	13	12	11	10	9	8	7	6	5	4	3	2	1	0
					rese	erved			1		P5	P4	P3	P2	P1	P0
Type Reset	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 1	RO 1	RO 1	RO 1	RO 1	RO 1
В	sit/Field		Nam	ne	Τv	pe	Reset	Description								
									•							
	31:6		reserv	ved	R	.0	0				rely on ti ure prodi					
											ead-mod				ou bit of	iodia bo
	5		P5		D	.O	0x1	32/6	M_Rit Wi	da Cana	aral Durn	ose Time	ar 5 Drac	ent		
	J		1 0	•	11	.0	OXI	32/0	32/64-Bit Wide General-Purpose Timer 5 Present							
								Val	ue Desc	•						
								1	32/64	4-bit wid	e genera	ıl-purpos	e timer r	module 5	is prese	ent.
								0	32/64	4-bit wid	e genera	ıl-purpos	e timer r	nodule 5	is not p	resent.
	4		P4		R	.0	0x1	32/6	64-Bit Wi	de Gene	eral-Purp	ose Time	er 4 Pres	sent		
								Val	ue Desc	rintion						
								1			e genera	ıl-purpos	e timer r	nodule 4	is prese	ent.
								0			e genera					
											Ü	• •			·	
	3		P3	}	R	0	0x1	32/6	64-Bit Wi	-Bit Wide General-Purpose Timer 3 Present						
								Val	ue Desc	rintion						
								1		•	e genera	ıl-purpos	e timer r	nodule 3	is prese	ent.
								0			e genera				•	
								ŭ	32.0	u	32	F P 30			P	···
	2		P2	!	R	.O	0x1	32/6	64-Bit Wi	de Gene	eral-Purp	ose Time	er 2 Pres	sent		
								Val	ue Desc	ription						
								1		•	e genera	ıl-purpos	e timer r	nodule 2	is prese	ent.
								•	30		320	F 5 P 50			- p. 550	

0

32/64-bit wide general-purpose timer module 2 is not present.

Bit/Field	Name	Type	Reset	Description			
1	P1	RO	0x1	32/64-Bit Wide General-Purpose Timer 1 Present			
				Value Description			
				1 32/64-bit wide general-purpose timer module 1 is present.			
				0 32/64-bit wide general-purpose timer module 1 is not present.			
0	P0	RO	0x1	32/64-Bit Wide General-Purpose Timer 0 Present			
				Value Description			
				1 32/64-bit wide general-purpose timer module 0 is present.			
				0 32/64-bit wide general-purpose timer module 0 is not present.			

Register 35: Watchdog Timer Software Reset (SRWD), offset 0x500

The **SRWD** register provides software the capability to reset the available watchdog modules. This register provides the same capability as the legacy **Software Reset Control n SRCRn** registers specifically for the watchdog modules and has the same bit polarity as the corresponding **SRCRn** bits.

A peripheral is reset by software using a simple two-step process:


- Software sets a bit (or bits) in the SRWD register. While the SRWD bit is 1, the peripheral is held in reset.
- 2. Software completes the reset process by clearing the **SRWD** bit.

There may be latency from the clearing of the **SRWD** bit to when the peripheral is ready for use. Software can check the corresponding **PRWD** bit to be sure.

Important: This register should be used to reset the watchdog modules. To support legacy software, the SRCR0 register is available. Setting a bit in the SRCR0 register also resets the corresponding module. Any bits that are changed by writing to the SRCR0 register can be read back correctly when reading the SRCR0 register. If software uses this register to reset a legacy peripheral (such as Watchdog 1), the write causes proper operation, but the value of that bit is not reflected in the SRCR0 register. If software uses both legacy and peripheral-specific register accesses, the peripheral-specific registers must be accessed by read-modify-write operations that affect only peripherals that are not present in the legacy registers. In this manner, both the peripheral-specific and legacy registers have coherent information.

Watchdog Timer Software Reset (SRWD)

Base 0x400F.E000 Offset 0x500 Type R/W, reset 0x0000.0000



Bit/Field	Name	Туре	Reset	Description
31:2	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
1	R1	R/W	0	Watchdog Timer 1 Software Reset

- 1 Watchdog module 1 is reset.
- 0 Watchdog module 1 is not reset.

Bit/Field	Name	Type	Reset	Description
0	R0	R/W	0	Watchdog Timer 0 Software Reset
				Value Description
				1 Watchdog module 0 is reset.
				0 Watchdog module 0 is not reset.

Register 36: 16/32-Bit General-Purpose Timer Software Reset (SRTIMER), offset 0x504

The **SRTIMER** register provides software the capability to reset the available 16/32-bit timer modules. This register provides the same capability as the legacy **Software Reset Control n SRCRn** registers specifically for the timer modules and has the same bit polarity as the corresponding **SRCRn** bits.

A peripheral is reset by software using a simple two-step process:


- 1. Software sets a bit (or bits) in the **SRTIMER** register. While the **SRTIMER** bit is 1, the peripheral is held in reset.
- 2. Software completes the reset process by clearing the **SRTIMER** bit.

There may be latency from the clearing of the **SRTIMER** bit to when the peripheral is ready for use. Software can check the corresponding **PRTIMER** bit to be sure.

Important: This register should be used to reset the timer modules. To support legacy software, the SRCR1 register is available. Setting a bit in the SRCR1 register also resets the corresponding module. Any bits that are changed by writing to the SRCR1 register can be read back correctly when reading the SRCR1 register. Software must use this register to reset modules that are not present in the legacy registers. If software uses this register to reset a legacy peripheral (such as Timer 1), the write causes proper operation, but the value of that bit is not reflected in the SRCR1 register. If software uses both legacy and peripheral-specific register accesses, the peripheral-specific registers must be accessed by read-modify-write operations that affect only peripherals that are not present in the legacy registers. In this manner, both the peripheral-specific and legacy registers have coherent information.

16/32-Bit General-Purpose Timer Software Reset (SRTIMER)

Base 0x400F.E000 Offset 0x504 Type R/W, reset 0x0000.0000



Bit/Field	Name	туре	Reset	Description
31:6	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
5	R5	R/W	0	16/32-Rit General-Purpose Timer 5 Software Reset

- 1 16/32-bit general-purpose timer module 5 is reset.
- 0 16/32-bit general-purpose timer module 5 is not reset.

Bit/Field	Name	Type	Reset	Description
4	R4	R/W	0	16/32-Bit General-Purpose Timer 4 Software Reset
				Value Description 1 16/32-bit general-purpose timer module 4 is reset.
				1 16/32-bit general-purpose timer module 4 is reset. 1 16/32-bit general-purpose timer module 4 is not reset.
3	R3	R/W	0	16/32-Bit General-Purpose Timer 3 Software Reset
				Value Description
				1 16/32-bit general-purpose timer module 3 is reset.
				0 16/32-bit general-purpose timer module 3 is not reset.
2	R2	R/W	0	16/32-Bit General-Purpose Timer 2 Software Reset
				Value Description
				1 16/32-bit general-purpose timer module 2 is reset.
				0 16/32-bit general-purpose timer module 2 is not reset.
1	R1	R/W	0	16/32-Bit General-Purpose Timer 1 Software Reset
				Value Description
				1 16/32-bit general-purpose timer module 1 is reset.
				0 16/32-bit general-purpose timer module 1 is not reset.
0	R0	R/W	0	16/32-Bit General-Purpose Timer 0 Software Reset
				Value Description
				1 16/32-bit general-purpose timer module 0 is reset.
				0 16/32-bit general-purpose timer module 0 is not reset.

Register 37: General-Purpose Input/Output Software Reset (SRGPIO), offset 0x508

The **SRGPIO** register provides software the capability to reset the available GPIO modules. This register provides the same capability as the legacy **Software Reset Control n SRCRn** registers specifically for the GPIO modules and has the same bit polarity as the corresponding **SRCRn** bits.

A peripheral is reset by software using a simple two-step process:

- 1. Software sets a bit (or bits) in the **SRGPIO** register. While the **SRGPIO** bit is 1, the peripheral is held in reset.
- 2. Software completes the reset process by clearing the **SRGPIO** bit.


There may be latency from the clearing of the **SRGPIO** bit to when the peripheral is ready for use. Software can check the corresponding **PRGPIO** bit to be sure.

Important: This register should be used to reset the GPIO modules. To support legacy software, the SRCR2 register is available. Setting a bit in the SRCR2 register also resets the corresponding module. Any bits that are changed by writing to the SRCR2 register can be read back correctly when reading the SRCR2 register. Software must use this register to reset modules that are not present in the legacy registers. If software uses this register to reset a legacy peripheral (such as GPIO A), the write causes proper operation, but the value of that bit is not reflected in the SRCR2 register. If software uses both legacy and peripheral-specific register accesses, the peripheral-specific registers must be accessed by read-modify-write operations that affect only peripherals that are not present in the legacy registers. In this manner, both the peripheral-specific and legacy registers have coherent information.

General-Purpose Input/Output Software Reset (SRGPIO)

Base 0x400F.E000 Offset 0x508

Type R/W, reset 0x0000.0000



Bit/Field	name	туре	Reset	Description
31:10	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
9	R9	R/W	0	GPIO Port K Software Reset

- 1 GPIO Port K is reset.
- 0 GPIO Port K is not reset.

Bit/Field	Name	Туре	Reset	Description
8	R8	R/W	0	GPIO Port J Software Reset
				Value Description GPIO Port J is reset. GPIO Port J is not reset.
7	R7	R/W	0	GPIO Port H Software Reset
				Value Description 1 GPIO Port H is reset. 0 GPIO Port H is not reset.
6	R6	R/W	0	GPIO Port G Software Reset
				Value Description 1 GPIO Port G is reset. 0 GPIO Port G is not reset.
5	R5	R/W	0	GPIO Port F Software Reset
				Value Description 1 GPIO Port F is reset. 0 GPIO Port F is not reset.
4	R4	R/W	0	GPIO Port E Software Reset
				Value Description 1 GPIO Port E is reset. 0 GPIO Port E is not reset.
3	R3	R/W	0	GPIO Port D Software Reset
				Value Description 1 GPIO Port D is reset. 0 GPIO Port D is not reset.
2	R2	R/W	0	GPIO Port C Software Reset
				Value Description 1 GPIO Port C is reset. 0 GPIO Port C is not reset.

Bit/Field	Name	Type	Reset	Description
1	R1	R/W	0	GPIO Port B Software Reset
				Value Description
				1 GPIO Port B is reset.
				0 GPIO Port B is not reset.
0	R0	R/W	0	GPIO Port A Software Reset
				Value Description
				1 GPIO Port A is reset.
				0 GPIO Port A is not reset.

Register 38: Micro Direct Memory Access Software Reset (SRDMA), offset 0x50C

The **SRDMA** register provides software the capability to reset the available μ DMA module. This register provides the same capability as the legacy **Software Reset Control n SRCRn** registers specifically for the μ DMA module and has the same bit polarity as the corresponding **SRCRn** bits.

A peripheral is reset by software using a simple two-step process:

- 1. Software sets a bit (or bits) in the **SRDMA** register. While the **SRDMA** bit is 1, the peripheral is held in reset.
- 2. Software completes the reset process by clearing the **SRDMA** bit.


There may be latency from the clearing of the **SRDMA** bit to when the peripheral is ready for use. Software can check the corresponding **PRDMA** bit to be sure.

Important: This register should be used to reset the μDMA module. To support legacy software, the SRCR2 register is available. Setting the UDMA bit in the SRCR2 register also resets the μDMA module. If the UDMA bit is set by writing to the SRCR2 register, it can be read back correctly when reading the SRCR2 register. If software uses this register to reset the μDMA module, the write causes proper operation, but the value of the UDMA bit is not reflected in the SRCR2 register. If software uses both legacy and peripheral-specific register accesses, the peripheral-specific registers must be accessed by read-modify-write operations that affect only peripherals that are not present in the legacy registers. In this manner, both the peripheral-specific and legacy registers have coherent information.

Micro Direct Memory Access Software Reset (SRDMA)

Base 0x400F.E000 Offset 0x50C

Type R/W, reset 0x0000.0000



Bit/Field	Name	Туре	Reset	Description
31:1	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
0	R0	R/W	0	μDMA Module Software Reset

- 1 μDMA module is reset.
- 0 μDMA module is not reset.

Register 39: Hibernation Software Reset (SRHIB), offset 0x514

The **SRHIB** register provides software the capability to reset the available Hibernation module. This register provides the same capability as the legacy **Software Reset Control n SRCRn** registers specifically for the Hibernation module and has the same bit polarity as the corresponding **SRCRn** bits.

A peripheral is reset by software using a simple two-step process:

- Software sets a bit (or bits) in the SRHIB register. While the SRHIB bit is 1, the peripheral is held in reset.
- 2. Software completes the reset process by clearing the SRHIB bit.


There may be latency from the clearing of the **SRHIB** bit to when the peripheral is ready for use. Software can check the corresponding **PRHIB** bit to be sure.

Important: This register should be used to reset the Hibernation module. To support legacy software, the SRCR0 register is available. Setting the HIB bit in the SRCR0 register also resets the Hibernation module. If the HIB bit is set by writing to the SRCR0 register, it can be read back correctly when reading the SRCR0 register. If software uses this register to reset the Hibernation module, the write causes proper operation, but the value of the HIB bit is not reflected in the SRCR0 register. If software uses both legacy and peripheral-specific register accesses, the peripheral-specific registers must be accessed by read-modify-write operations that affect only peripherals that are not present in the legacy registers. In this manner, both the peripheral-specific and legacy registers have coherent information.

Hibernation Software Reset (SRHIB)

Base 0x400F.E000 Offset 0x514

Type R/W, reset 0x0000.0000



Bit/Field	Name	Type	Reset	Description
31:1	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
0	R0	R/W	0	Hibernation Module Software Reset

- 1 Hibernation module is reset.
- 0 Hibernation module is not reset.

Register 40: Universal Asynchronous Receiver/Transmitter Software Reset (SRUART), offset 0x518

The **SRUART** register provides software the capability to reset the available UART modules. This register provides the same capability as the legacy **Software Reset Control n SRCRn** registers specifically for the UART modules and has the same bit polarity as the corresponding **SRCRn** bits.

A peripheral is reset by software using a simple two-step process:

- 1. Software sets a bit (or bits) in the **SRUART** register. While the **SRUART** bit is 1, the peripheral is held in reset.
- 2. Software completes the reset process by clearing the SRUART bit.


There may be latency from the clearing of the **SRUART** bit to when the peripheral is ready for use. Software can check the corresponding **PRUART** bit to be sure.

Important: This register should be used to reset the UART modules. To support legacy software, the SRCR1 register is available. Setting a bit in the SRCR1 register also resets the corresponding module. Any bits that are changed by writing to the SRCR1 register can be read back correctly when reading the SRCR1 register. Software must use this register to reset modules that are not present in the legacy registers. If software uses this register to reset a legacy peripheral (such as UART0), the write causes proper operation, but the value of that bit is not reflected in the SRCR1 register. If software uses both legacy and peripheral-specific register accesses, the peripheral-specific registers must be accessed by read-modify-write operations that affect only peripherals that are not present in the legacy registers. In this manner, both the peripheral-specific and legacy registers have coherent information.

Universal Asynchronous Receiver/Transmitter Software Reset (SRUART)

Base 0x400F.E000 Offset 0x518

Type R/W, reset 0x0000.0000



Bit/Field	Name	Type	Reset	Description
31:8	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
7	R7	R/W	0	UART Module 7 Software Reset

- 1 UART module 7 is reset.
- 0 UART module 7 is not reset.

Bit/Field	Name	Туре	Reset	Description
6	R6	R/W	0	UART Module 6 Software Reset
				Value Description
				1 UART module 6 is reset.
				0 UART module 6 is not reset.
5	R5	R/W	0	UART Module 5 Software Reset
				Value Description
				1 UART module 5 is reset.
				0 UART module 5 is not reset.
4	R4	R/W	0	UART Module 4 Software Reset
				Value Description
				1 UART module 4 is reset.
				0 UART module 4 is not reset.
3	R3	R/W	0	UART Module 3 Software Reset
				Value Description
				1 UART module 3 is reset.
				0 UART module 3 is not reset.
2	R2	R/W	0	UART Module 2 Software Reset
				Value Description
				1 UART module 2 is reset.
				0 UART module 2 is not reset.
1	R1	R/W	0	UART Module 1 Software Reset
				Value Description
				1 UART module 1 is reset.
				0 UART module 1 is not reset.
0	R0	R/W	0	UART Module 0 Software Reset
				Value Description
				1 UART module 0 is reset.
				0 UART module 0 is not reset.

Register 41: Synchronous Serial Interface Software Reset (SRSSI), offset 0x51C

The **SRSSI** register provides software the capability to reset the available SSI modules. This register provides the same capability as the legacy **Software Reset Control n SRCRn** registers specifically for the SSI modules and has the same bit polarity as the corresponding **SRCRn** bits.

A peripheral is reset by software using a simple two-step process:

- 1. Software sets a bit (or bits) in the **SRSSI** register. While the **SRSSI** bit is 1, the peripheral is held in reset.
- 2. Software completes the reset process by clearing the SRSSI bit.


There may be latency from the clearing of the **SRSSI** bit to when the peripheral is ready for use. Software can check the corresponding **PRSSI** bit to be sure.

Important: This register should be used to reset the SSI modules. To support legacy software, the SRCR1 register is available. Setting a bit in the SRCR1 register also resets the corresponding module. Any bits that are changed by writing to the SRCR1 register can be read back correctly when reading the SRCR1 register. Software must use this register to reset modules that are not present in the legacy registers. If software uses this register to reset a legacy peripheral (such as SSI0), the write causes proper operation, but the value of that bit is not reflected in the SRCR1 register. If software uses both legacy and peripheral-specific register accesses, the peripheral-specific registers must be accessed by read-modify-write operations that affect only peripherals that are not present in the legacy registers. In this manner, both the peripheral-specific and legacy registers have coherent information.

Synchronous Serial Interface Software Reset (SRSSI)

Base 0x400F.E000 Offset 0x51C

Type R/W, reset 0x0000.0000



Bit/Field	Name	Type	Reset	Description
31:4	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
3	R3	R/W	0	SSI Module 3 Software Reset

- 1 SSI module 3 is reset.
- 0 SSI module 3 is not reset.

Bit/Field	Name	Туре	Reset	Description
2	R2	R/W	0	SSI Module 2 Software Reset
				Value Description 1 SSI module 2 is reset. 0 SSI module 2 is not reset.
1	R1	R/W	0	SSI Module 1 Software Reset
				Value Description 1 SSI module 1 is reset. 0 SSI module 1 is not reset.
0	R0	R/W	0	SSI Module 0 Software Reset
				Value Description
				1 SSI module 0 is reset.
				0 SSI module 0 is not reset.

Register 42: Inter-Integrated Circuit Software Reset (SRI2C), offset 0x520

The **SRI2C** register provides software the capability to reset the available I²C modules. This register provides the same capability as the legacy **Software Reset Control n SRCRn** registers specifically for the I²C modules and has the same bit polarity as the corresponding **SRCRn** bits.

A peripheral is reset by software using a simple two-step process:

- Software sets a bit (or bits) in the SRI2C register. While the SRI2C bit is 1, the peripheral is held in reset.
- 2. Software completes the reset process by clearing the SRI2C bit.


There may be latency from the clearing of the **SRI2C** bit to when the peripheral is ready for use. Software can check the corresponding **PRI2C** bit to be sure.

Important: This register should be used to reset the I²C modules. To support legacy software, the SRCR1 register is available. Setting a bit in the SRCR1 register also resets the corresponding module. Any bits that are changed by writing to the SRCR1 register can be read back correctly when reading the SRCR1 register. Software must use this register to reset modules that are not present in the legacy registers. If software uses this register to reset a legacy peripheral (such as I2C0), the write causes proper operation, but the value of that bit is not reflected in the SRCR1 register. If software uses both legacy and peripheral-specific register accesses, the peripheral-specific registers must be accessed by read-modify-write operations that affect only peripherals that are not present in the legacy registers. In this manner, both the peripheral-specific and legacy registers have coherent information.

Inter-Integrated Circuit Software Reset (SRI2C)

Base 0x400F.E000 Offset 0x520

Type R/W, reset 0x0000.0000



Bit/Field	Name	Type	Reset	Description
31:6	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
5	R5	R/W	0	I ² C Module 5 Software Reset

- 1 I²C module 5 is reset.
- 0 I²C module 5 is not reset

Bit/Field	Name	Туре	Reset	Description
4	R4	R/W	0	I ² C Module 4 Software Reset
				Value Description 1 I ² C module 4 is reset. 0 I ² C module 4 is not reset.
3	R3	R/W	0	I ² C Module 3 Software Reset
				Value Description
				1 I ² C module 3 is reset.
				0 I ² C module 3 is not reset.
2	R2	R/W	0	I ² C Module 2 Software Reset
				Value Description
				1 I ² C module 2 is reset.
				0 I ² C module 2 is not reset.
1	R1	R/W	0	I ² C Module 1 Software Reset
				Value Description
				1 I ² C module 1 is reset.
				0 I ² C module 1 is not reset.
0	R0	R/W	0	I ² C Module 0 Software Reset
				Value Description
				1 I ² C module 0 is reset.
				0 I ² C module 0 is not reset.

Register 43: Universal Serial Bus Software Reset (SRUSB), offset 0x528

The **SRUSB** register provides software the capability to reset the available USB module. This register provides the same capability as the legacy **Software Reset Control n SRCRn** registers specifically for the USB module and has the same bit polarity as the corresponding **SRCRn** bits.

A peripheral is reset by software using a simple two-step process:

- Software sets a bit (or bits) in the SRUSB register. While the SRUSB bit is 1, the peripheral is held in reset.
- Software completes the reset process by clearing the SRUSB bit.


There may be latency from the clearing of the **SRUSB** bit to when the peripheral is ready for use. Software can check the corresponding **PRUSB** bit to be sure.

Important: This register should be used to reset the USB module. To support legacy software, the SRCR2 register is available. Setting the USB0 bit in the SRCR2 register also resets the USB module. If the USB0 bit is set by writing to the SRCR2 register, it can be read back correctly when reading the SRCR2 register. If software uses this register to reset the USB module, the write causes proper operation, but the value of the USB0 bit is not reflected in the SRCR2 register. If software uses both legacy and peripheral-specific register accesses, the peripheral-specific registers must be accessed by read-modify-write operations that affect only peripherals that are not present in the legacy registers. In this manner, both the peripheral-specific and legacy registers have coherent information.

Universal Serial Bus Software Reset (SRUSB)

Base 0x400F.E000 Offset 0x528

Type R/W, reset 0x0000.0000



Bit/Field	Name	Туре	Reset	Description
31:1	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
0	R0	R/W	0	USB Module Software Reset

- 1 USB module is reset.
- 0 USB module is not reset.

Register 44: Controller Area Network Software Reset (SRCAN), offset 0x534

The **SRCAN** register provides software the capability to reset the available CAN modules. This register provides the same capability as the legacy **Software Reset Control n SRCRn** registers specifically for the CAN modules and has the same bit polarity as the corresponding **SRCRn** bits.

A peripheral is reset by software using a simple two-step process:

- Software sets a bit (or bits) in the SRCAN register. While the SRCAN bit is 1, the peripheral is held in reset.
- 2. Software completes the reset process by clearing the SRCAN bit.


There may be latency from the clearing of the **SRCAN** bit to when the peripheral is ready for use. Software can check the corresponding **PRCAN** bit to be sure.

Important: This register should be used to reset the CAN modules. To support legacy software, the SRCR0 register is available. Setting a bit in the SRCR0 register also resets the corresponding module. Any bits that are changed by writing to the SRCR0 register can be read back correctly when reading the SRCR0 register. If software uses this register to reset a legacy peripheral (such as CAN0), the write causes proper operation, but the value of that bit is not reflected in the SRCR0 register. If software uses both legacy and peripheral-specific register accesses, the peripheral-specific registers must be accessed by read-modify-write operations that affect only peripherals that are not present in the legacy registers. In this manner, both the peripheral-specific and legacy registers have coherent information.

Controller Area Network Software Reset (SRCAN)

Base 0x400F.E000 Offset 0x534

Type R/W, reset 0x0000.0000



Bit/Field	Name	Type	Reset	Description
31:2	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
1	R1	R/W	0	CAN Module 1 Software Reset

- 1 CAN module 1 is reset.
- 0 CAN module 1 is not reset.

Bit/Field	Name	Туре	Reset	Description
0	R0	R/W	0	CAN Module 0 Software Reset
				Value Description
				1 CAN module 0 is reset.
				0 CAN module 0 is not reset.

Register 45: Analog-to-Digital Converter Software Reset (SRADC), offset 0x538

The **SRADC** register provides software the capability to reset the available ADC modules. This register provides the same capability as the legacy **Software Reset Control n SRCRn** registers specifically for the ADC modules and has the same bit polarity as the corresponding **SRCRn** bits.

A peripheral is reset by software using a simple two-step process:

- Software sets a bit (or bits) in the SRADC register. While the SRADC bit is 1, the peripheral is held in reset.
- 2. Software completes the reset process by clearing the **SRADC** bit.


There may be latency from the clearing of the **SRADC** bit to when the peripheral is ready for use. Software can check the corresponding **PRADC** bit to be sure.

Important: This register should be used to reset the ADC modules. To support legacy software, the SRCR0 register is available. Setting a bit in the SRCR0 register also resets the corresponding module. Any bits that are changed by writing to the SRCR0 register can be read back correctly when reading the SRCR0 register. If software uses this register to reset a legacy peripheral (such as ADC0), the write causes proper operation, but the value of that bit is not reflected in the SRCR0 register. If software uses both legacy and peripheral-specific register accesses, the peripheral-specific registers must be accessed by read-modify-write operations that affect only peripherals that are not present in the legacy registers. In this manner, both the peripheral-specific and legacy registers have coherent information.

Analog-to-Digital Converter Software Reset (SRADC)

Base 0x400F.E000 Offset 0x538

Type R/W, reset 0x0000.0000



Bit/Field	Name	Type	Reset	Description
31:2	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
1	R1	R/W	0	ADC Module 1 Software Reset

- 1 ADC module 1 is reset.
- 0 ADC module 1 is not reset.

Bit/Field	Name	Туре	Reset	Description
0	R0	R/W	0	ADC Module 0 Software Reset
				Value Description
				1 ADC module 0 is reset.
				0 ADC module 0 is not reset.

Register 46: Analog Comparator Software Reset (SRACMP), offset 0x53C

The **SRACMP** register provides software the capability to reset the available analog comparator module. This register provides the same capability as the legacy **Software Reset Control n SRCRn** registers specifically for the analog comparator module and has the same bit polarity as the corresponding **SRCRn** bits.

A block is reset by software using a simple two-step process:


- Software sets a bit (or bits) in the SRACMP register. While the SRACMP bit is 1, the module
 is held in reset.
- 2. Software completes the reset process by clearing the **SRACMP** bit.

There may be latency from the clearing of the **SRACMP** bit to when the module is ready for use. Software can check the corresponding **PRACMP** bit to be sure.

Important: This register should be used to reset the analog comparator module. To support legacy software, the SRCR1 register is available. Setting any of the COMPn bits in the SRCR0 register also resets the analog comparator module. If any of the COMPn bits are set by writing to the SRCR1 register, it can be read back correctly when reading the SRCR0 register. If software uses this register to reset the analog comparator module, the write causes proper operation, but the value of R0 is not reflected by the COMPn bits in the SRCR1 register. If software uses both legacy and peripheral-specific register accesses, the peripheral-specific registers must be accessed by read-modify-write operations that affect only peripherals that are not present in the legacy registers. In this manner, both the peripheral-specific and legacy registers have coherent information.

Analog Comparator Software Reset (SRACMP)

Base 0x400F.E000 Offset 0x53C



Bit/Field	Name	Type	Reset	Description
31:1	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
0	R0	R/W	0	Analog Comparator Module 0 Software Reset

- 1 Analog comparator module is reset.
- 0 Analog comparator module is not reset.

Register 47: Pulse Width Modulator Software Reset (SRPWM), offset 0x540

The **SRPWM** register provides software the capability to reset the available PWM modules. This register provides the same capability as the legacy **Software Reset Control n SRCRn** registers specifically for the PWM modules and has the same bit polarity as the corresponding **SRCRn** bits.

A peripheral is reset by software using a simple two-step process:

- 1. Software sets a bit (or bits) in the **SRPWM** register. While the **SRPWM** bit is 1, the peripheral is held in reset.
- 2. Software completes the reset process by clearing the **SRPWM** bit.


There may be latency from the clearing of the **SRPWM** bit to when the peripheral is ready for use. Software can check the corresponding **PRPWM** bit to be sure.

Important: This register should be used to reset the PWM modules. To support legacy software, the SRCR0 register is available. Setting the PWM bit in the SRCR0 register also resets the PWM0 module. If the PWM bit is changed by writing to the SRCR0 register, it can be read back correctly when reading the SRCR0 register. Software must use this register to reset PWM1, which is not present in the legacy registers. If software uses this register to reset PWM0, the write causes proper operation, but the value of that bit is not reflected in the SRCR0 register. If software uses both legacy and peripheral-specific register accesses, the peripheral-specific registers must be accessed by read-modify-write operations that affect only peripherals that are not present in the legacy registers. In this manner, both the peripheral-specific and legacy registers have coherent information.

Pulse Width Modulator Software Reset (SRPWM)

Base 0x400F.E000 Offset 0x540

Type R/W, reset 0x0000.0000



Bit/Field	Name	Туре	Reset	Description
31:2	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
1	R1	R/W	0	PWM Module 1 Software Reset

- 1 PWM module 1 is reset.
- 0 PWM module 1 is not reset.

Bit/Field	Name	Туре	Reset	Description
0	R0	R/W	0	PWM Module 0 Software Reset
				Value Description
				1 PWM module 0 is reset.
				0 PWM module 0 is not reset.

Register 48: Quadrature Encoder Interface Software Reset (SRQEI), offset 0x544

The **SRQEI** register provides software the capability to reset the available QEI modules. This register provides the same capability as the legacy Software Reset Control n SRCRn registers specifically for the QEI modules and has the same bit polarity as the corresponding **SRCRn** bits.

A peripheral is reset by software using a simple two-step process:

- 1. Software sets a bit (or bits) in the SRQEI register. While the SRQEI bit is 1, the peripheral is held in reset.
- Software completes the reset process by clearing the **SRQEI** bit.


There may be latency from the clearing of the **SRQEI** bit to when the peripheral is ready for use. Software can check the corresponding **PRQEI** bit to be sure.

Important: This register should be used to reset the QEI modules. To support legacy software, the SRCR1 register is available. Setting a bit in the SRCR1 register also resets the corresponding module. Any bits that are changed by writing to the SRCR1 register can be read back correctly when reading the **SRCR1** register. If software uses this register to reset a legacy peripheral (such as QEI0), the write causes proper operation, but the value of that bit is not reflected in the SRCR1 register. If software uses both legacy and peripheral-specific register accesses, the peripheral-specific registers must be accessed by read-modify-write operations that affect only peripherals that are not present in the legacy registers. In this manner, both the peripheral-specific and legacy registers have coherent information.

Quadrature Encoder Interface Software Reset (SRQEI)

Base 0x400F.E000

Offset 0x544 Type R/W, reset 0x0000.0000



Bit/Field	Name	Туре	Reset	Description
31:2	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
1	R1	R/W	0	QEI Module 1 Software Reset

- 1 QEI module 1 is reset.
- 0 QEI module 1 is not reset.

Bit/Field	Name	Type	Reset	Description
0	R0	R/W	0	QEI Module 0 Software Reset
				Value Description 1 QEI module 0 is reset. 0 QEI module 0 is not reset.

Register 49: EEPROM Software Reset (SREEPROM), offset 0x558

The **SREEPROM** register provides software the capability to reset the available EEPROM module.

A peripheral is reset by software using a simple two-step process:


- 1. Software sets a bit (or bits) in the **SREEPROM** register. While the **SREEPROM** bit is 1, the peripheral is held in reset.
- 2. Software completes the reset process by clearing the **SREEPROM** bit.

There may be latency from the clearing of the **SREEPROM** bit to when the peripheral is ready for use. Software can check the corresponding **PREEPROM** bit to be sure.

EEPROM Software Reset (SREEPROM)

Base 0x400F.E000 Offset 0x558

Type R/W, reset 0x0000.0000



Bit/Field	Name	Туре	Reset	Description
31:1	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
0	R0	R/W	0	EEPROM Module Software Reset

- 1 EEPROM module is reset.
- 0 EEPROM module is not reset.

Register 50: 32/64-Bit Wide General-Purpose Timer Software Reset (SRWTIMER), offset 0x55C

The **SRWTIMER** register provides software the capability to reset the available 32/64-bit wide timer modules.

A peripheral is reset by software using a simple two-step process:


- 1. Software sets a bit (or bits) in the **SRWTIMER** register. While the **SRWTIMER** bit is 1, the peripheral is held in reset.
- 2. Software completes the reset process by clearing the **SRWTIMER** bit.

There may be latency from the clearing of the **SRWTIMER** bit to when the peripheral is ready for use. Software can check the corresponding **PRWTIMER** bit to be sure.

32/64-Bit Wide General-Purpose Timer Software Reset (SRWTIMER)

Base 0x400F.E000 Offset 0x55C

Type R/W, reset 0x0000.0000



Bit/Field	Name	Туре	Reset	Description
31:6	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
5	R5	R/W	0	32/64-Bit Wide General-Purpose Timer 5 Software Reset
				Value Description
				1 32/64-bit wide general-purpose timer module 5 is reset.
				0 32/64-bit wide general-purpose timer module 5 is not reset.
4	R4	R/W	0	32/64-Bit Wide General-Purpose Timer 4 Software Reset
				Value Description
				1 32/64-bit wide general-purpose timer module 4 is reset.
				0 32/64-bit wide general-purpose timer module 4 is not reset.
3	R3	R/W	0	32/64-Bit Wide General-Purpose Timer 3 Software Reset
				Value Description
				1 32/64-bit wide general-purpose timer module 3 is reset.

0

32/64-bit wide general-purpose timer module 3 is not reset.

Bit/Field	Name	Type	Reset	Description
2	R2	R/W	0	32/64-Bit Wide General-Purpose Timer 2 Software Reset
				Value Description 1 32/64-bit wide general-purpose timer module 2 is reset. 0 32/64-bit wide general-purpose timer module 2 is not reset.
1	R1	R/W	0	32/64-Bit Wide General-Purpose Timer 1 Software Reset Value Description
				1 32/64-bit wide general-purpose timer module 1 is reset.
				0 32/64-bit wide general-purpose timer module 1 is not reset.
0	R0	R/W	0	32/64-Bit Wide General-Purpose Timer 0 Software Reset
				Value Description
				1 32/64-bit wide general-purpose timer module 0 is reset.
				0 32/64-bit wide general-purpose timer module 0 is not reset.

Register 51: Watchdog Timer Run Mode Clock Gating Control (RCGCWD), offset 0x600


The **RCGCWD** register provides software the capability to enable and disable watchdog modules in Run mode. When enabled, a module is provided a clock and accesses to module registers are allowed. When disabled, the clock is disabled to save power and accesses to module registers generate a bus fault. This register provides the same capability as the legacy **Run Mode Clock Gating Control Register n RCGCn** registers specifically for the watchdog modules and has the same bit polarity as the corresponding **RCGCn** bits.

Important: This register should be used to control the clocking for the watchdog modules. To support legacy software, the RCGC0 register is available. A write to the RCGC0 register also writes the corresponding bit in this register. Any bits that are changed by writing to the RCGC0 register can be read back correctly with a read of the RCGC0 register. If software uses this register to write a legacy peripheral (such as Watchdog 0), the write causes proper operation, but the value of that bit is not reflected in the RCGC0 register. If software uses both legacy and peripheral-specific register accesses, the peripheral-specific registers must be accessed by read-modify-write operations that affect only peripherals that are not present in the legacy registers. In this manner, both the peripheral-specific and legacy registers have coherent information.

Watchdog Timer Run Mode Clock Gating Control (RCGCWD)

Base 0x400F.E000 Offset 0x600

Type R/W, reset 0x0000.0000



Bit/Field	Name	Туре	Reset	Description
31:2	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
1	R1	R/W	0	Watchdog Timer 1 Run Mode Clock Gating Control Value Description Enable and provide a clock to Watchdog module 1 in Run mode. Watchdog module 1 is disabled.
0	R0	R/W	0	Watchdog Timer 0 Run Mode Clock Gating Control

- 1 Enable and provide a clock to Watchdog module 0 in Run mode.
- 0 Watchdog module 0 is disabled.


Register 52: 16/32-Bit General-Purpose Timer Run Mode Clock Gating Control (RCGCTIMER), offset 0x604


The **RCGCTIMER** register provides software the capability to enable and disable 16/32-bit timer modules in Run mode. When enabled, a module is provided a clock and accesses to module registers are allowed. When disabled, the clock is disabled to save power and accesses to module registers generate a bus fault. This register provides the same capability as the legacy **Run Mode Clock Gating Control Register n RCGCn** registers specifically for the timer modules and has the same bit polarity as the corresponding **RCGCn** bits.

Important: This register should be used to control the clocking for the timer modules. To support legacy software, the RCGC1 register is available. A write to the RCGC1 register also writes the corresponding bit in this register. Any bits that are changed by writing to the RCGC1 register can be read back correctly with a read of the RCGC1 register. Software must use this register to support modules that are not present in the legacy registers. If software uses this register to write a legacy peripheral (such as Timer 0), the write causes proper operation, but the value of that bit is not reflected in the RCGC1 register. If software uses both legacy and peripheral-specific register accesses, the peripheral-specific registers must be accessed by read-modify-write operations that affect only peripherals that are not present in the legacy registers. In this manner, both the peripheral-specific and legacy registers have coherent information.

16/32-Bit General-Purpose Timer Run Mode Clock Gating Control (RCGCTIMER)

Base 0x400F.E000 Offset 0x604





Bit/Field	Name	Type	Reset	Description
31:6	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
5	R5	R/W	0	16/32-Bit General-Purpose Timer 5 Run Mode Clock Gating Control

- Enable and provide a clock to 16/32-bit general-purpose timer module 5 in Run mode.
- 0 16/32-bit general-purpose timer module 5 is disabled.

Bit/Field	Name	Туре	Reset	Description
4	R4	R/W	0	16/32-Bit General-Purpose Timer 4 Run Mode Clock Gating Control
				Value Description
				Enable and provide a clock to 16/32-bit general-purpose timer module 4 in Run mode.
				0 16/32-bit general-purpose timer module 4 is disabled.
3	R3	R/W	0	16/32-Bit General-Purpose Timer 3 Run Mode Clock Gating Control
				Value Description
				Enable and provide a clock to 16/32-bit general-purpose timer module 3 in Run mode.
				0 16/32-bit general-purpose timer module 3 is disabled.
2	R2	R/W	0	16/32-Bit General-Purpose Timer 2 Run Mode Clock Gating Control
				Value Description
				Enable and provide a clock to 16/32-bit general-purpose timer module 2 in Run mode.
				0 16/32-bit general-purpose timer module 2 is disabled.
1	R1	R/W	0	16/32-Bit General-Purpose Timer 1 Run Mode Clock Gating Control
				Value Description
				Enable and provide a clock to 16/32-bit general-purpose timer module 1 in Run mode.
				0 16/32-bit general-purpose timer module 1 is disabled.
0	R0	R/W	0	16/32-Bit General-Purpose Timer 0 Run Mode Clock Gating Control
				Value Description
				Enable and provide a clock to 16/32-bit general-purpose timer module 0 in Run mode.
				0 16/32-bit general-purpose timer module 0 is disabled.

February 20, 2013 329

Register 53: General-Purpose Input/Output Run Mode Clock Gating Control (RCGCGPIO), offset 0x608


The **RCGCGPIO** register provides software the capability to enable and disable GPIO modules in Run mode. When enabled, a module is provided a clock and accesses to module registers are allowed. When disabled, the clock is disabled to save power and accesses to module registers generate a bus fault. This register provides the same capability as the legacy **Run Mode Clock Gating Control Register n RCGCn** registers specifically for the watchdog modules and has the same bit polarity as the corresponding **RCGCn** bits.

Important: This register should be used to control the clocking for the GPIO modules. To support legacy software, the RCGC2 register is available. A write to the RCGC2 register also writes the corresponding bit in this register. Any bits that are changed by writing to the RCGC2 register can be read back correctly with a read of the RCGC2 register. Software must use this register to support modules that are not present in the legacy registers. If software uses this register to write a legacy peripheral (such as GPIO A), the write causes proper operation, but the value of that bit is not reflected in the RCGC2 register. If software uses both legacy and peripheral-specific register accesses, the peripheral-specific registers must be accessed by read-modify-write operations that affect only peripherals that are not present in the legacy registers. In this manner, both the peripheral-specific and legacy registers have coherent information.

General-Purpose Input/Output Run Mode Clock Gating Control (RCGCGPIO)

Base 0x400F.E000 Offset 0x608

Type R/W, reset 0x0000.0000



Bit/Field	Name	Туре	Reset	Description
31:10	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
9	R9	R/W	0	GPIO Port K Run Mode Clock Gating Control
				Value Description
				1 Enable and provide a clock to GPIO Port K in Run mode.
				0 GPIO Port K is disabled.
8	R8	R/W	0	GPIO Port J Run Mode Clock Gating Control
				Value Description
				1 Enable and provide a clock to GPIO Port J in Run mode.

0

GPIO Port J is disabled.

Bit/Field	Name	Туре	Reset	Description
7	R7	R/W	0	GPIO Port H Run Mode Clock Gating Control
				Value Description
				Enable and provide a clock to GPIO Port H in Run mode.GPIO Port H is disabled.
				U GFIO POIL IT IS disabled.
6	R6	R/W	0	GPIO Port G Run Mode Clock Gating Control
				Value Description
				1 Enable and provide a clock to GPIO Port G in Run mode.
				0 GPIO Port G is disabled.
5	R5	R/W	0	GPIO Port F Run Mode Clock Gating Control
				Value Description
				1 Enable and provide a clock to GPIO Port F in Run mode.
				0 GPIO Port F is disabled.
4	R4	R/W	0	GPIO Port E Run Mode Clock Gating Control
				Value Description
				1 Enable and provide a clock to GPIO Port E in Run mode.
				0 GPIO Port E is disabled.
3	R3	R/W	0	GPIO Port D Run Mode Clock Gating Control
				Value Description
				1 Enable and provide a clock to GPIO Port D in Run mode.
				0 GPIO Port D is disabled.
2	R2	R/W	0	GPIO Port C Run Mode Clock Gating Control
				Value Description
				1 Enable and provide a clock to GPIO Port C in Run mode.
				0 GPIO Port C is disabled.
1	R1	R/W	0	GPIO Port B Run Mode Clock Gating Control
				Value Description
				1 Enable and provide a clock to GPIO Port B in Run mode.
				0 GPIO Port B is disabled.

February 20, 2013 331

Bit/Field	Name	Type	Reset	Description
0	R0	R/W	0	GPIO Port A Run Mode Clock Gating Control
				Value Description
				1 Enable and provide a clock to GPIO Port A in Run mode.
				0 GPIO Port A is disabled.

Register 54: Micro Direct Memory Access Run Mode Clock Gating Control (RCGCDMA), offset 0x60C

The **RCGCDMA** register provides software the capability to enable and disable the µDMA module in Run mode. When enabled, the module is provided a clock and accesses to module registers are allowed. When disabled, the clock is disabled to save power and accesses to module registers generate a bus fault. This register provides the same capability as the legacy **Run Mode Clock Gating Control Register n RCGCn** registers specifically for the watchdog modules and has the same bit polarity as the corresponding **RCGCn** bits.


Important: This register should be used to control the clocking for the μDMA module. To support legacy software, the RCGC2 register is available. A write to the UDMA bit in the RCGC2 register also writes the R0 bit in this register. If the UDMA bit is changed by writing to the RCGC2 register, it can be read back correctly with a read of the RCGC2 register. If software uses this register to control the clock for the μDMA module, the write causes proper operation, but the UDMA bit in the RCGC2 register does not reflect the value of the R0 bit. If software uses both legacy and peripheral-specific register accesses, the peripheral-specific registers must be accessed by read-modify-write operations that affect only peripherals that are not present in the legacy registers. In this manner, both

the peripheral-specific and legacy registers have coherent information.

Micro Direct Memory Access Run Mode Clock Gating Control (RCGCDMA)

Base 0x400F.E000 Offset 0x60C

Type R/W, reset 0x0000.0000



Bit/Field	Name	Туре	Reset	Description
31:1	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
0	RO	R/M	0	uDMA Module Run Mode Clock Gating Control

- 1 Enable and provide a clock to the μDMA module in Run mode.
- 0 μDMA module is disabled.

Register 55: Hibernation Run Mode Clock Gating Control (RCGCHIB), offset 0x614


The **RCGCHIB** register provides software the capability to enable and disable the Hibernation module in Run mode. When enabled, the module is provided a clock and accesses to module registers are allowed. When disabled, the clock is disabled to save power and accesses to module registers generate a bus fault. This register provides the same capability as the legacy **Run Mode Clock Gating Control Register n RCGCn** registers specifically for the watchdog modules and has the same bit polarity as the corresponding **RCGCn** bits.

Important: This register should be used to control the clocking for the Hibernation module. To support legacy software, the RCGC0 register is available. A write to the HIB bit in the RCGC0 register also writes the R0 bit in this register. If the HIB bit is changed by writing to the RCGC0 register, it can be read back correctly with a read of the RCGC0 register. If software uses this register to control the clock for the Hibernation module, the write causes proper operation, but the HIB bit in the RCGC0 register does not reflect the value of the R0 bit. If software uses both legacy and peripheral-specific register accesses, the peripheral-specific registers must be accessed by read-modify-write operations that affect only peripherals that are not present in the legacy registers. In this manner, both the peripheral-specific and legacy registers have coherent information.

Hibernation Run Mode Clock Gating Control (RCGCHIB)

Base 0x400F.E000 Offset 0x614

Type R/W, reset 0x0000.0001



Bit/Field	Name	Туре	Reset	Description
31:1	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
0	R0	R/W	1	Hibernation Module Run Mode Clock Gating Control

- Enable and provide a clock to the Hibernation module in Run mode.
- 0 Hibernation module is disabled.

Register 56: Universal Asynchronous Receiver/Transmitter Run Mode Clock Gating Control (RCGCUART), offset 0x618


The **RCGCUART** register provides software the capability to enable and disable the UART modules in Run mode. When enabled, a module is provided a clock and accesses to module registers are allowed. When disabled, the clock is disabled to save power and accesses to module registers generate a bus fault. This register provides the same capability as the legacy **Run Mode Clock Gating Control Register n RCGCn** registers specifically for the watchdog modules and has the same bit polarity as the corresponding **RCGCn** bits.

Important: This register should be used to control the clocking for the UART modules. To support legacy software, the RCGC1 register is available. A write to the RCGC1 register also writes the corresponding bit in this register. Any bits that are changed by writing to the RCGC1 register can be read back correctly with a read of the RCGC1 register. Software must use this register to support modules that are not present in the legacy registers. If software uses this register to write a legacy peripheral (such as UART0), the write causes proper operation, but the value of that bit is not reflected in the RCGC1 register. If software uses both legacy and peripheral-specific register accesses, the peripheral-specific registers must be accessed by read-modify-write operations that affect only peripherals that are not present in the legacy registers. In this manner, both the peripheral-specific and legacy registers have coherent information.

Universal Asynchronous Receiver/Transmitter Run Mode Clock Gating Control (RCGCUART)

Base 0x400F.E000 Offset 0x618

Type R/W, reset 0x0000.0000



Bit/Field	Name	Туре	Reset	Description
31:8	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
7	R7	R/W	0	UART Module 7 Run Mode Clock Gating Control
				Value Description 1 Enable and provide a clock to UART module 7 in Run mode.
				0 UART module 7 is disabled.
6	R6	R/W	0	UART Module 6 Run Mode Clock Gating Control
				Value Description

February 20, 2013 335

0

Enable and provide a clock to UART module 6 in Run mode.

UART module 6 is disabled.

Bit/Field	Name	Туре	Reset	Description
5	R5	R/W	0	UART Module 5 Run Mode Clock Gating Control
				Value Description 1 Enable and provide a clock to UART module 5 in Run mode. 0 UART module 5 is disabled.
4	R4	R/W	0	UART Module 4 Run Mode Clock Gating Control
				Value Description 1 Enable and provide a clock to UART module 4 in Run mode. 0 UART module 4 is disabled.
3	R3	R/W	0	UART Module 3 Run Mode Clock Gating Control
				Value Description 1 Enable and provide a clock to UART module 3 in Run mode. 0 UART module 3 is disabled.
2	R2	R/W	0	UART Module 2 Run Mode Clock Gating Control Value Description 1 Enable and provide a clock to UART module 2 in Run mode.
				0 UART module 2 is disabled.
1	R1	R/W	0	UART Module 1 Run Mode Clock Gating Control Value Description Enable and provide a clock to UART module 1 in Run mode. UART module 1 is disabled.
0	R0	R/W	0	UART Module 0 Run Mode Clock Gating Control Value Description 1 Enable and provide a clock to UART module 0 in Run mode. 0 UART module 0 is disabled.

336 February 20, 2013

Register 57: Synchronous Serial Interface Run Mode Clock Gating Control (RCGCSSI), offset 0x61C


The **RCGCSSI** register provides software the capability to enable and disable the SSI modules in Run mode. When enabled, a module is provided a clock and accesses to module registers are allowed. When disabled, the clock is disabled to save power and accesses to module registers generate a bus fault. This register provides the same capability as the legacy **Run Mode Clock Gating Control Register n RCGCn** registers specifically for the watchdog modules and has the same bit polarity as the corresponding **RCGCn** bits.

Important: This register should be used to control the clocking for the SSI modules. To support legacy software, the RCGC1 register is available. A write to the RCGC1 register also writes the corresponding bit in this register. Any bits that are changed by writing to the RCGC1 register can be read back correctly with a read of the RCGC1 register. Software must use this register to support modules that are not present in the legacy registers. If software uses this register to write a legacy peripheral (such as SSI0), the write causes proper operation, but the value of that bit is not reflected in the RCGC1 register. If software uses both legacy and peripheral-specific register accesses, the peripheral-specific registers must be accessed by read-modify-write operations that affect only peripherals that are not present in the legacy registers. In this manner, both the peripheral-specific and legacy registers have coherent information.

Synchronous Serial Interface Run Mode Clock Gating Control (RCGCSSI)

Base 0x400F.E000 Offset 0x61C

Type R/W, reset 0x0000.0000



Bit/Field	Name	Туре	Reset	Description
31:4	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
3	R3	R/W	0	SSI Module 3 Run Mode Clock Gating Control
				Value Description
				1 Enable and provide a clock to SSI module 3 in Run mode.
				0 SSI module 3 is disabled.
2	R2	R/W	0	SSI Module 2 Run Mode Clock Gating Control
				Value Description

February 20, 2013 337

1

Enable and provide a clock to SSI module 2 in Run mode.

SSI module 2 is disabled.

Bit/Field	Name	Type	Reset	Description
1	R1	R/W	0	SSI Module 1 Run Mode Clock Gating Control
				Value Description
				1 Enable and provide a clock to SSI module 1 in Run mode.
				0 SSI module 1 is disabled.
0	R0	R/W	0	SSI Module 0 Run Mode Clock Gating Control
				Value Description
				1 Enable and provide a clock to SSI module 0 in Run mode.
				0 SSI module 0 is disabled.

Register 58: Inter-Integrated Circuit Run Mode Clock Gating Control (RCGCI2C), offset 0x620


The **RCGCI2C** register provides software the capability to enable and disable the I²C modules in Run mode. When enabled, a module is provided a clock and accesses to module registers are allowed. When disabled, the clock is disabled to save power and accesses to module registers generate a bus fault. This register provides the same capability as the legacy **Run Mode Clock Gating Control Register n RCGCn** registers specifically for the watchdog modules and has the same bit polarity as the corresponding **RCGCn** bits.

Important: This register should be used to control the clocking for the I²C modules. To support legacy software, the RCGC1 register is available. A write to the RCGC1 register also writes the corresponding bit in this register. Any bits that are changed by writing to the RCGC1 register can be read back correctly with a read of the RCGC1 register. Software must use this register to support modules that are not present in the legacy registers. If software uses this register to write a legacy peripheral (such as I2C0), the write causes proper operation, but the value of that bit is not reflected in the RCGC1 register. If software uses both legacy and peripheral-specific register accesses, the peripheral-specific registers must be accessed by read-modify-write operations that affect only peripherals that are not present in the legacy registers. In this manner, both the peripheral-specific and legacy registers have coherent information.

Inter-Integrated Circuit Run Mode Clock Gating Control (RCGCI2C)

Base 0x400F.E000

Offset 0x620 Type R/W, reset 0x0000.0000



Bit/Field	Name	Туре	Reset	Description
31:6	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
5	R5	R/W	0	I ² C Module 5 Run Mode Clock Gating Control
				Value Description 1 Enable and provide a clock to I ² C module 5 in Run mode. 0 I ² C module 5 is disabled.
4	R4	R/W	0	I ² C Module 4 Run Mode Clock Gating Control

- 1 Enable and provide a clock to I²C module 4 in Run mode.
- 0 I²C module 4 is disabled.

Bit/Field	Name	Туре	Reset	Description
3	R3	R/W	0	I ² C Module 3 Run Mode Clock Gating Control
				Value Description 1 Enable and provide a clock to I ² C module 3 in Run mode. 0 I ² C module 3 is disabled.
2	R2	R/W	0	I ² C Module 2 Run Mode Clock Gating Control Value Description 1 Enable and provide a clock to I ² C module 2 in Run mode. 0 I ² C module 2 is disabled.
1	R1	R/W	0	I ² C Module 1 Run Mode Clock Gating Control Value Description 1 Enable and provide a clock to I ² C module 1 in Run mode. 0 I ² C module 1 is disabled.
0	R0	R/W	0	I ² C Module 0 Run Mode Clock Gating Control Value Description 1 Enable and provide a clock to I ² C module 0 in Run mode. 0 I ² C module 0 is disabled.

Register 59: Universal Serial Bus Run Mode Clock Gating Control (RCGCUSB), offset 0x628

The **RCGCUSB** register provides software the capability to enable and disable the USB module in Run mode. When enabled, the module is provided a clock and accesses to module registers are allowed. When disabled, the clock is disabled to save power and accesses to module registers generate a bus fault. This register provides the same capability as the legacy **Run Mode Clock Gating Control Register n RCGCn** registers specifically for the watchdog modules and has the same bit polarity as the corresponding **RCGCn** bits.


Important: This register should be used to control the clocking for the USB module. To support legacy software, the RCGC2 register is available. A write to the USB0 bit in the RCGC2 register also writes the R0 bit in this register. If the USB0 bit is changed by writing to the RCGC2 register, it can be read back correctly with a read of the RCGC2 register. If software uses this register to control the clock for the USB module, the write causes proper operation, but the USB0 bit in the RCGC2 register does not reflect the value of the R0 bit. If software uses both legacy and peripheral-specific register accesses, the peripheral-specific registers must be accessed by read-modify-write operations that affect only peripherals that are not present in the legacy registers. In this manner, both

the peripheral-specific and legacy registers have coherent information.

Universal Serial Bus Run Mode Clock Gating Control (RCGCUSB)

Base 0x400F.E000 Offset 0x628

Type R/W, reset 0x0000.0000



Bit/Field	Name	Туре	Reset	Description
31:1	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
0	R0	R/W	0	USB Module Run Mode Clock Gating Control

- 1 Enable and provide a clock to the USB module in Run mode.
- 0 USB module is disabled.

Register 60: Controller Area Network Run Mode Clock Gating Control (RCGCCAN), offset 0x634


The **RCGCCAN** register provides software the capability to enable and disable the CAN modules in Run mode. When enabled, a module is provided a clock and accesses to module registers are allowed. When disabled, the clock is disabled to save power and accesses to module registers generate a bus fault. This register provides the same capability as the legacy **Run Mode Clock Gating Control Register n RCGCn** registers specifically for the watchdog modules and has the same bit polarity as the corresponding **RCGCn** bits.

Important: This register should be used to control the clocking for the CAN modules. To support legacy software, the RCGC0 register is available. A write to the RCGC0 register also writes the corresponding bit in this register. Any bits that are changed by writing to the RCGC0 register can be read back correctly with a read of the RCGC0 register. If software uses this register to write a legacy peripheral (such as CAN0), the write causes proper operation, but the value of that bit is not reflected in the RCGC0 register. If software uses both legacy and peripheral-specific register accesses, the peripheral-specific registers must be accessed by read-modify-write operations that affect only peripherals that are not present in the legacy registers. In this manner, both the peripheral-specific and legacy registers have coherent information.

Controller Area Network Run Mode Clock Gating Control (RCGCCAN)

Base 0x400F.E000 Offset 0x634

Type R/W, reset 0x0000.0000



Bit/Field	Name	Туре	Reset	Description
31:2	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
1	R1	R/W	0	CAN Module 1 Run Mode Clock Gating Control
				Value Description 1 Enable and provide a clock to CAN module 1 in Run mode. 0 CAN module 1 is disabled.
0	R0	R/W	0	CAN Module 0 Run Mode Clock Gating Control

- 1 Enable and provide a clock to CAN module 0 in Run mode.
- 0 CAN module 0 is disabled.

Register 61: Analog-to-Digital Converter Run Mode Clock Gating Control (RCGCADC), offset 0x638


The **RCGCADC** register provides software the capability to enable and disable the ADC modules in Run mode. When enabled, a module is provided a clock and accesses to module registers are allowed. When disabled, the clock is disabled to save power and accesses to module registers generate a bus fault. This register provides the same capability as the legacy **Run Mode Clock Gating Control Register n RCGCn** registers specifically for the watchdog modules and has the same bit polarity as the corresponding **RCGCn** bits.

Important: This register should be used to control the clocking for the ADC modules. To support legacy software, the RCGC0 register is available. A write to the RCGC0 register also writes the corresponding bit in this register. Any bits that are changed by writing to the RCGC0 register can be read back correctly with a read of the RCGC0 register. If software uses this register to write a legacy peripheral (such as ADC0), the write causes proper operation, but the value of that bit is not reflected in the RCGC0 register. If software uses both legacy and peripheral-specific register accesses, the peripheral-specific registers must be accessed by read-modify-write operations that affect only peripherals that are not present in the legacy registers. In this manner, both the peripheral-specific and legacy registers have coherent information.

Analog-to-Digital Converter Run Mode Clock Gating Control (RCGCADC)

Base 0x400F.E000 Offset 0x638

Type R/W, reset 0x0000.0000



Bit/Field	Name	Туре	Reset	Description
31:2	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
1	R1	R/W	0	ADC Module 1 Run Mode Clock Gating Control Value Description Enable and provide a clock to ADC module 1 in Run mode. ADC module 1 is disabled.
0	R0	R/W	0	ADC Module 0 Run Mode Clock Gating Control

- 1 Enable and provide a clock to ADC module 0 in Run mode.
- 0 ADC module 0 is disabled.

Register 62: Analog Comparator Run Mode Clock Gating Control (RCGCACMP), offset 0x63C


The RCGCACMP register provides software the capability to enable and disable the analog comparator module in Run mode. When enabled, the module is provided a clock and accesses to module registers are allowed. When disabled, the clock is disabled to save power and accesses to module registers generate a bus fault. This register provides the same capability as the legacy Run Mode Clock Gating Control Register n RCGCn registers specifically for the watchdog modules and has the same bit polarity as the corresponding **RCGCn** bits.

Important: This register should be used to control the clocking for the analog comparator module. To support legacy software, the RCGC1 register is available. Setting any of the COMPn bits in the RCGC1 register also sets the R0 bit in this register. If any of the COMPn bits are set by writing to the RCGC1 register, it can be read back correctly when reading the RCGC1 register. If software uses this register to change the clocking for the analog comparator module, the write causes proper operation, but the value R0 is not reflected by the COMPn bits in the RCGC1 register. If software uses both legacy and peripheral-specific register accesses, the peripheral-specific registers must be accessed by read-modify-write operations that affect only peripherals that are not present in the legacy registers. In this manner, both the peripheral-specific and legacy registers have coherent information.

Analog Comparator Run Mode Clock Gating Control (RCGCACMP)

Offset 0x63C

Type R/W, reset 0x0000.0000



Bit/Field	Name	Type	Reset	Description
31:1	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
0	R0	R/W	0	Analog Comparator Module 0 Run Mode Clock Gating Control

- 1 Enable and provide a clock to the analog comparator module in Run mode.
- 0 Analog comparator module is disabled.

Register 63: Pulse Width Modulator Run Mode Clock Gating Control (RCGCPWM), offset 0x640

The **RCGCPWM** register provides software the capability to enable and disable the PWM modules in Run mode. When enabled, a module is provided a clock and accesses to module registers are allowed. When disabled, the clock is disabled to save power and accesses to module registers generate a bus fault. This register provides the same capability as the legacy **Run Mode Clock Gating Control Register n RCGCn** registers specifically for the watchdog modules and has the same bit polarity as the corresponding **RCGCn** bits.


Important: This register should be used to control the clocking for the PWM modules. To support legacy software, the RCGC0 register is available. A write to the PWM bit in the RCGC0 register also writes the R0 bit in this register. If the PWM bit is changed by writing to the RCGC0 register, it can be read back correctly with a read of the RCGC0 register. Software must use this register to support modules that are not present in the legacy registers. If software uses this register to write to R0, the write causes proper operation, but the value of that bit is not reflected in the PWM bit in the RCGC0 register. If software uses both legacy and peripheral-specific register accesses, the peripheral-specific registers must be accessed by read-modify-write operations that affect only peripherals that are not present in the legacy registers. In this manner, both the peripheral-specific and legacy registers have coherent information.

Pulse Width Modulator Run Mode Clock Gating Control (RCGCPWM)

Base 0x400F.E000

Offset 0x640

Type R/W, reset 0x0000.0000



Bit/Field	Name	Туре	Reset	Description
31:2	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
1	R1	R/W	0	PWM Module 1 Run Mode Clock Gating Control
				Value Description 1 Enable and provide a clock to PWM module 1 in Run mode. 0 PWM module 1 is disabled.
0	R0	R/W	0	PWM Module 0 Run Mode Clock Gating Control

- 1 Enable and provide a clock to PWM module 0 in Run mode.
- 0 PWM module 0 is disabled.

Register 64: Quadrature Encoder Interface Run Mode Clock Gating Control (RCGCQEI), offset 0x644


The **RCGCQEI** register provides software the capability to enable and disable the QEI modules in Run mode. When enabled, a module is provided a clock and accesses to module registers are allowed. When disabled, the clock is disabled to save power and accesses to module registers generate a bus fault. This register provides the same capability as the legacy **Run Mode Clock Gating Control Register n RCGCn** registers specifically for the watchdog modules and has the same bit polarity as the corresponding **RCGCn** bits.

Important: This register should be used to control the clocking for the QEI modules. To support legacy software, the RCGC1 register is available. A write to the RCGC1 register also writes the corresponding bit in this register. Any bits that are changed by writing to the RCGC1 register can be read back correctly with a read of the RCGC1 register. If software uses this register to write a legacy peripheral (such as QEI0), the write causes proper operation, but the value of that bit is not reflected in the RCGC1 register. If software uses both legacy and peripheral-specific register accesses, the peripheral-specific registers must be accessed by read-modify-write operations that affect only peripherals that are not present in the legacy registers. In this manner, both the peripheral-specific and legacy registers have coherent information.

Quadrature Encoder Interface Run Mode Clock Gating Control (RCGCQEI)

Base 0x400F.E000 Offset 0x644

Type R/W, reset 0x0000.0000



Bit/Field	Name	Туре	Reset	Description
31:2	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
1	R1	R/W	0	QEI Module 1 Run Mode Clock Gating Control
				Value Description 1 Enable and provide a clock to QEI module 1 in Run mode. 0 QEI module 1 is disabled.
0	R0	R/W	0	QEI Module 0 Run Mode Clock Gating Control

- 1 Enable and provide a clock to QEI module 0 in Run mode.
- 0 QEI module 0 is disabled.


Register 65: EEPROM Run Mode Clock Gating Control (RCGCEEPROM), offset 0x658

The **RCGCEEPROM** register provides software the capability to enable and disable the EEPROM module in Run mode. When enabled, the module is provided a clock and accesses to module registers are allowed. When disabled, the clock is disabled to save power and accesses to module registers generate a bus fault.

EEPROM Run Mode Clock Gating Control (RCGCEEPROM)

Base 0x400F.E000 Offset 0x658

Type R/W, reset 0x0000.0000



Bit/Field	Name	Type	Reset	Description
31:1	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
0	R0	R/W	0	EEPROM Module Run Mode Clock Gating Control

- 1 Enable and provide a clock to the EEPROM module in Run mode
- 0 EEPROM module is disabled.


Register 66: 32/64-Bit Wide General-Purpose Timer Run Mode Clock Gating Control (RCGCWTIMER), offset 0x65C

The RCGCWTIMER register provides software the capability to enable and disable 3264-bit timer modules in Run mode. When enabled, a module is provided a clock and accesses to module registers are allowed. When disabled, the clock is disabled to save power and accesses to module registers generate a bus fault. This register provides the same capability as the legacy Run Mode Clock Gating Control Register n RCGCn registers specifically for the timer modules and has the same bit polarity as the corresponding RCGCn bits.

32/64-Bit Wide General-Purpose Timer Run Mode Clock Gating Control (RCGCWTIMER)

Base 0x400F.E000 Offset 0x65C

Type R/W, reset 0x0000.0000



Bit/Field	Name	Type	Reset	Description
31:6	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
5	R5	R/W	0	32/64-Bit Wide General-Purpose Timer 5 Run Mode Clock Gating Control
				Value Description
				1 Enable and provide a clock to 32/64-bit wide general-purpose timer module 5 in Run mode.
				0 32/64-bit wide general-purpose timer module 5 is disabled.
4	R4	R/W	0	32/64-Bit Wide General-Purpose Timer 4 Run Mode Clock Gating Control
				Value Description
				1 Enable and provide a clock to 32/64-bit wide general-purpose timer module 4 in Run mode.
				0 32/64-bit wide general-purpose timer module 4 is disabled.
3	R3	R/W	0	32/64-Bit Wide General-Purpose Timer 3 Run Mode Clock Gating Control
				Value Description

- Enable and provide a clock to 32/64-bit wide general-purpose timer module 3 in Run mode.
- 32/64-bit wide general-purpose timer module 3 is disabled.

Bit/Field	Name	Туре	Reset	Description
2	R2	R/W	0	32/64-Bit Wide General-Purpose Timer 2 Run Mode Clock Gating Control
				Value Description
				1 Enable and provide a clock to 32/64-bit wide general-purpose timer module 2 in Run mode.
				0 32/64-bit wide general-purpose timer module 2 is disabled.
1	R1	R/W	0	32/64-Bit Wide General-Purpose Timer 1 Run Mode Clock Gating Control
				Value Description
				1 Enable and provide a clock to 32/64-bit wide general-purpose timer module 1 in Run mode.
				0 32/64-bit wide general-purpose timer module 1 is disabled.
0	R0	R/W	0	32/64-Bit Wide General-Purpose Timer 0 Run Mode Clock Gating Control
				Value Description
				1 Enable and provide a clock to 32/64-bit wide general-purpose timer module 0 in Run mode.
				0 32/64-bit wide general-purpose timer module 0 is disabled.

Register 67: Watchdog Timer Sleep Mode Clock Gating Control (SCGCWD), offset 0x700

The **SCGCWD** register provides software the capability to enable and disable watchdog modules in sleep mode. When enabled, a module is provided a clock. When disabled, the clock is disabled to save power. This register provides the same capability as the legacy **Sleep Mode Clock Gating Control Register n SCGCn** registers specifically for the watchdog modules and has the same bit polarity as the corresponding **SCGCn** bits.

Important: This register should be used to control the clocking for the watchdog modules. To support legacy software, the SCGC0 register is available. A write to the SCGC0 register also writes the corresponding bit in this register. Any bits that are changed by writing to the SCGC0 register can be read back correctly with a read of the SCGC0 register. If software uses this register to write a legacy peripheral (such as Watchdog 0), the write causes proper operation, but the value of that bit is not reflected in the SCGC0 register. If software uses both legacy and peripheral-specific register accesses, the peripheral-specific registers must be accessed by read-modify-write operations that affect only peripherals that are not present in the legacy registers. In this manner, both the peripheral-specific and legacy registers have coherent information.

Watchdog Timer Sleep Mode Clock Gating Control (SCGCWD)

Base 0x400F.E000 Offset 0x700 Type R/W, reset 0x0000.0000

	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16
								rese	rved							•
Туре	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO						
Reset	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0
	15	14	13	12	11	10	9	8	7	6	5	4	3	2	1	0
							rese	rved							S1	S0
Туре	RO	RO	RO	RO	RO	RO	RO	RO	R/W	R/W						
Reset	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0

Bit/Field	Name	Туре	Reset	Description
31:2	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
1	S1	R/W	0	Watchdog Timer 1 Sleep Mode Clock Gating Control
				Value Description
				1 Enable and provide a clock to Watchdog module 1 in sleep mode.
				0 Watchdog module 1 is disabled.
0	S0	R/W	0	Watchdog Timer 0 Sleep Mode Clock Gating Control
				Value Description
				Enable and provide a clock to Watchdog module 0 in sleep mode.
				0 Watchdog module 0 is disabled.

Register 68: 16/32-Bit General-Purpose Timer Sleep Mode Clock Gating Control (SCGCTIMER), offset 0x704


The **SCGCTIMER** register provides software the capability to enable and disable 16/32-bit timer modules in sleep mode. When enabled, a module is provided a clock. When disabled, the clock is disabled to save power. This register provides the same capability as the legacy **Sleep Mode Clock Gating Control Register n SCGCn** registers specifically for the timer modules and has the same bit polarity as the corresponding **SCGCn** bits.

Important: This register should be used to control the clocking for the timer modules. To support legacy software, the SCGC1 register is available. A write to the SCGC1 register also writes the corresponding bit in this register. Any bits that are changed by writing to the SCGC1 register can be read back correctly with a read of the SCGC1 register. Software must use this register to support modules that are not present in the legacy registers. If software uses this register to write a legacy peripheral (such as Timer 0), the write causes proper operation, but the value of that bit is not reflected in the SCGC1 register. If software uses both legacy and peripheral-specific register accesses, the peripheral-specific registers must be accessed by read-modify-write operations that affect only peripherals that are not present in the legacy registers. In this manner, both the peripheral-specific and legacy registers have coherent information.

16/32-Bit General-Purpose Timer Sleep Mode Clock Gating Control (SCGCTIMER)

Base 0x400F.E000 Offset 0x704

Type R/W, reset 0x0000.0000



Bit/Field	Name	Туре	Reset	Description
31:6	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
5	S5	R/W	0	16/32-Bit General-Purpose Timer 5 Sleep Mode Clock Gating Control
				Value Description
				Enable and provide a clock to 16/32-bit general-purpose timer module 5 in sleep mode.
				0 16/32-bit general-purpose timer module 5 is disabled.
4	S4	R/W	0	16/32-Bit General-Purpose Timer 4 Sleep Mode Clock Gating Control
				Value Description
				1 Enable and provide a clock to 16/32-bit general-purpose timer

February 20, 2013 351

0

module 4 in sleep mode.

16/32-bit general-purpose timer module 4 is disabled.

Bit/Field	Name	Type	Reset	Description
3	S3	R/W	0	16/32-Bit General-Purpose Timer 3 Sleep Mode Clock Gating Control
				Value Description
				1 Enable and provide a clock to 16/32-bit general-purpose timer module 3 in sleep mode.
				0 16/32-bit general-purpose timer module 3 is disabled.
2	S2	R/W	0	16/32-Bit General-Purpose Timer 2 Sleep Mode Clock Gating Control
				Value Description 1 Enable and provide a clock to 16/32-bit general-purpose timer
				 Enable and provide a clock to 16/32-bit general-purpose timer module 2 in sleep mode.
				0 16/32-bit general-purpose timer module 2 is disabled.
1	S1	R/W	0	16/32-Bit General-Purpose Timer 1 Sleep Mode Clock Gating Control
				Value Description
				1 Enable and provide a clock to 16/32-bit general-purpose timer module 1 in sleep mode.
				0 16/32-bit general-purpose timer module 1 is disabled.
0	S0	R/W	0	16/32-Bit General-Purpose Timer 0 Sleep Mode Clock Gating Control
				Value Description
				Enable and provide a clock to 16/32-bit general-purpose timer module 0 in sleep mode.
				0 16/32-bit general-purpose timer module 0 is disabled.

Register 69: General-Purpose Input/Output Sleep Mode Clock Gating Control (SCGCGPIO), offset 0x708

The **SCGCGPIO** register provides software the capability to enable and disable GPIO modules in sleep mode. When enabled, a module is provided a clock. When disabled, the clock is disabled to save power. This register provides the same capability as the legacy **Sleep Mode Clock Gating Control Register n SCGCn** registers specifically for the watchdog modules and has the same bit polarity as the corresponding **SCGCn** bits.


Important: This register should be used to control the clocking for the GPIO modules. To support legacy software, the SCGC2 register is available. A write to the SCGC2 register also writes the corresponding bit in this register. Any bits that are changed by writing to the SCGC2 register can be read back correctly with a read of the SCGC2 register. Software must use this register to support modules that are not present in the legacy registers. If software uses this register to write a legacy peripheral (such as GPIO A), the write causes proper operation, but the value of that bit is not reflected in the SCGC2 register. If software uses both legacy and peripheral-specific register accesses, the peripheral-specific registers must be accessed by read-modify-write operations that affect only peripherals that are not present in the legacy registers. In this manner, both

the peripheral-specific and legacy registers have coherent information.

General-Purpose Input/Output Sleep Mode Clock Gating Control (SCGCGPIO)

Base 0x400F.E000 Offset 0x708

Type R/W, reset 0x0000.0000



Bit/Field	Name	Туре	Reset	Description
31:10	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
9	S9	R/W	0	GPIO Port K Sleep Mode Clock Gating Control Value Description Enable and provide a clock to GPIO Port K in sleep mode. GPIO Port K is disabled.
8	S8	R/W	0	GPIO Port J Sleep Mode Clock Gating Control

- 1 Enable and provide a clock to GPIO Port J in sleep mode.
- 0 GPIO Port J is disabled.

Bit/Field	Name	Туре	Reset	Description
7	S7	R/W	0	GPIO Port H Sleep Mode Clock Gating Control
				Value Description
				1 Enable and provide a clock to GPIO Port H in sleep mode.
				0 GPIO Port H is disabled.
6	S6	R/W	0	GPIO Port G Sleep Mode Clock Gating Control
				Value Description
				1 Enable and provide a clock to GPIO Port G in sleep mode.
				0 GPIO Port G is disabled.
5	S5	R/W	0	GPIO Port F Sleep Mode Clock Gating Control
				Value Description
				1 Enable and provide a clock to GPIO Port F in sleep mode.
				0 GPIO Port F is disabled.
4	S4	R/W	0	GPIO Port E Sleep Mode Clock Gating Control
				Value Description
				1 Enable and provide a clock to GPIO Port E in sleep mode.
				0 GPIO Port E is disabled.
3	S3	R/W	0	GPIO Port D Sleep Mode Clock Gating Control
				Value Description
				1 Enable and provide a clock to GPIO Port D in sleep mode.
				0 GPIO Port D is disabled.
2	S2	R/W	0	GPIO Port C Sleep Mode Clock Gating Control
				Value Description
				1 Enable and provide a clock to GPIO Port C in sleep mode.
				0 GPIO Port C is disabled.
1	S1	R/W	0	GPIO Port B Sleep Mode Clock Gating Control
				Value Description
				1 Enable and provide a clock to GPIO Port B in sleep mode.
				0 GPIO Port B is disabled.

Bit/Field	Name	Туре	Reset	Description
0	S0	R/W	0	GPIO Port A Sleep Mode Clock Gating Control
				Value Description 1 Enable and provide a clock to GPIO Port A in sleep mode. 0 GPIO Port A is disabled.

February 20, 2013 355

Register 70: Micro Direct Memory Access Sleep Mode Clock Gating Control (SCGCDMA), offset 0x70C


The SCGCDMA register provides software the capability to enable and disable the µDMA module in sleep mode. When enabled, a module is provided a clock. When disabled, the clock is disabled to save power. This register provides the same capability as the legacy Sleep Mode Clock Gating Control Register n SCGCn registers specifically for the watchdog modules and has the same bit polarity as the corresponding SCGCn bits.

Important: This register should be used to control the clocking for the μDMA module. To support legacy software, the SCGC2 register is available. A write to the UDMA bit in the SCGC2 register also writes the S0 bit in this register. If the UDMA bit is changed by writing to the SCGC2 register, it can be read back correctly with a read of the SCGC2 register. If software uses this register to control the clock for the µDMA module, the write causes proper operation, but the UDMA bit in the SCGC2 register does not reflect the value of the S0 bit. If software uses both legacy and peripheral-specific register accesses, the peripheral-specific registers must be accessed by read-modify-write operations that affect only peripherals that are not present in the legacy registers. In this manner, both the peripheral-specific and legacy registers have coherent information.

Micro Direct Memory Access Sleep Mode Clock Gating Control (SCGCDMA)

Base 0x400F.E000 Offset 0x70C

Type R/W, reset 0x0000.0000



Bit/Field	Name	Type	Reset	Description
31:1	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
0	S0	R/W	0	μDMA Module Sleep Mode Clock Gating Control

- 1 Enable and provide a clock to the µDMA module in sleep mode.
- 0 µDMA module is disabled.

Register 71: Hibernation Sleep Mode Clock Gating Control (SCGCHIB), offset 0x714


The **SCGCHIB** register provides software the capability to enable and disable the Hibernation module in sleep mode. When enabled, a module is provided a clock. When disabled, the clock is disabled to save power. This register provides the same capability as the legacy **Sleep Mode Clock Gating Control Register n SCGCn** registers specifically for the watchdog modules and has the same bit polarity as the corresponding **SCGCn** bits.

Important: This register should be used to control the clocking for the Hibernation module. To support legacy software, the SCGC0 register is available. A write to the HIB bit in the SCGC0 register also writes the S0 bit in this register. If the HIB bit is changed by writing to the SCGC0 register, it can be read back correctly with a read of the SCGC0 register. If software uses this register to control the clock for the Hibernation module, the write causes proper operation, but the HIB bit in the SCGC0 register does not reflect the value of the S0 bit. If software uses both legacy and peripheral-specific register accesses, the peripheral-specific registers must be accessed by read-modify-write operations that affect only peripherals that are not present in the legacy registers. In this manner, both the peripheral-specific and legacy registers have coherent information.

Hibernation Sleep Mode Clock Gating Control (SCGCHIB)

Base 0x400F.E000 Offset 0x714

Type R/W, reset 0x0000.0001



Bit/Field	Name	Type	Reset	Description
31:1	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
0	S0	R/W	1	Hibernation Module Sleep Mode Clock Gating Control

- Enable and provide a clock to the Hibernation module in sleep mode.
- 0 Hibernation module is disabled.

Register 72: Universal Asynchronous Receiver/Transmitter Sleep Mode Clock Gating Control (SCGCUART), offset 0x718


The **SCGCUART** register provides software the capability to enable and disable the UART modules in sleep mode. When enabled, a module is provided a clock. When disabled, the clock is disabled to save power. This register provides the same capability as the legacy **Sleep Mode Clock Gating Control Register n SCGCn** registers specifically for the watchdog modules and has the same bit polarity as the corresponding **SCGCn** bits.

Important: This register should be used to control the clocking for the UART modules. To support legacy software, the SCGC1 register is available. A write to the SCGC1 register also writes the corresponding bit in this register. Any bits that are changed by writing to the SCGC1 register can be read back correctly with a read of the SCGC1 register. Software must use this register to support modules that are not present in the legacy registers. If software uses this register to write a legacy peripheral (such as UART0), the write causes proper operation, but the value of that bit is not reflected in the SCGC1 register. If software uses both legacy and peripheral-specific register accesses, the peripheral-specific registers must be accessed by read-modify-write operations that affect only peripherals that are not present in the legacy registers. In this manner, both the peripheral-specific and legacy registers have coherent information.

Universal Asynchronous Receiver/Transmitter Sleep Mode Clock Gating Control (SCGCUART)

Base 0x400F.E000 Offset 0x718

Type R/W, reset 0x0000.0000



Bit/Field	Name	Туре	Reset	Description
31:8	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
7	S7	R/W	0	UART Module 7 Sleep Mode Clock Gating Control Value Description Enable and provide a clock to UART module 7 in sleep mode. UART module 7 is disabled.
6	S6	R/W	0	UART Module 6 Sleep Mode Clock Gating Control

- 1 Enable and provide a clock to UART module 6 in sleep mode.
- 0 UART module 6 is disabled.

Bit/Field	Name	Туре	Reset	Description
5	S5	R/W	0	UART Module 5 Sleep Mode Clock Gating Control
				Value Description 1 Enable and provide a clock to UART module 5 in sleep mode. 0 UART module 5 is disabled.
4	S4	R/W	0	UART Module 4 Sleep Mode Clock Gating Control
				Value Description 1 Enable and provide a clock to UART module 4 in sleep mode. 0 UART module 4 is disabled.
3	S3	R/W	0	UART Module 3 Sleep Mode Clock Gating Control
				Value Description 1 Enable and provide a clock to UART module 3 in sleep mode. 0 UART module 3 is disabled.
2	S2	R/W	0	UART Module 2 Sleep Mode Clock Gating Control
				Value Description 1 Enable and provide a clock to UART module 2 in sleep mode. 0 UART module 2 is disabled.
1	S1	R/W	0	UART Module 1 Sleep Mode Clock Gating Control
				Value Description 1 Enable and provide a clock to UART module 1 in sleep mode. 0 UART module 1 is disabled.
0	SO	R/W	0	UART Module 0 Sleep Mode Clock Gating Control Value Description 1 Enable and provide a clock to UART module 0 in sleep mode. 0 UART module 0 is disabled.

February 20, 2013 359

Register 73: Synchronous Serial Interface Sleep Mode Clock Gating Control (SCGCSSI), offset 0x71C


The **SCGCSSI** register provides software the capability to enable and disable the SSI modules in sleep mode. When enabled, a module is provided a clock. When disabled, the clock is disabled to save power. This register provides the same capability as the legacy **Sleep Mode Clock Gating Control Register n SCGCn** registers specifically for the watchdog modules and has the same bit polarity as the corresponding **SCGCn** bits.

Important: This register should be used to control the clocking for the SSI modules. To support legacy software, the SCGC1 register is available. A write to the SCGC1 register also writes the corresponding bit in this register. Any bits that are changed by writing to the SCGC1 register can be read back correctly with a read of the SCGC1 register. Software must use this register to support modules that are not present in the legacy registers. If software uses this register to write a legacy peripheral (such as SSI0), the write causes proper operation, but the value of that bit is not reflected in the SCGC1 register. If software uses both legacy and peripheral-specific register accesses, the peripheral-specific registers must be accessed by read-modify-write operations that affect only peripherals that are not present in the legacy registers. In this manner, both the peripheral-specific and legacy registers have coherent information.

Synchronous Serial Interface Sleep Mode Clock Gating Control (SCGCSSI)

Base 0x400F.E000 Offset 0x71C

Type R/W, reset 0x0000.0000



Bit/Field	Name	Туре	Reset	Description
31:4	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
3	S3	R/W	0	SSI Module 3 Sleep Mode Clock Gating Control
				Value Description Enable and provide a clock to SSI module 3 in sleep mode. SSI module 3 is disabled.
2	S2	R/W	0	SSI Module 2 Sleep Mode Clock Gating Control

- 1 Enable and provide a clock to SSI module 2 in sleep mode.
- 0 SSI module 2 is disabled.

Bit/Field	Name	Type	Reset	Description
1	S1	R/W	0	SSI Module 1 Sleep Mode Clock Gating Control
				Value Description
				1 Enable and provide a clock to SSI module 1 in sleep mode.
				0 SSI module 1 is disabled.
0	S0	R/W	0	SSI Module 0 Sleep Mode Clock Gating Control
				Value Description
				1 Enable and provide a clock to SSI module 0 in sleep mode.
				0 SSI module 0 is disabled.

February 20, 2013 361

Register 74: Inter-Integrated Circuit Sleep Mode Clock Gating Control (SCGCI2C), offset 0x720


The **SCGCI2C** register provides software the capability to enable and disable the I²C modules in sleep mode. When enabled, a module is provided a clock. When disabled, the clock is disabled to save power. This register provides the same capability as the legacy **Sleep Mode Clock Gating Control Register n SCGCn** registers specifically for the watchdog modules and has the same bit polarity as the corresponding **SCGCn** bits.

Important: This register should be used to control the clocking for the I²C modules. To support legacy software, the SCGC1 register is available. A write to the SCGC1 register also writes the corresponding bit in this register. Any bits that are changed by writing to the SCGC1 register can be read back correctly with a read of the SCGC1 register. Software must use this register to support modules that are not present in the legacy registers. If software uses this register to write a legacy peripheral (such as I²CO), the write causes proper operation, but the value of that bit is not reflected in the SCGC1 register. If software uses both legacy and peripheral-specific register accesses, the peripheral-specific registers must be accessed by read-modify-write operations that affect only peripherals that are not present in the legacy registers. In this manner, both the peripheral-specific and legacy registers have coherent information.

Inter-Integrated Circuit Sleep Mode Clock Gating Control (SCGCI2C)

Base 0x400F.E000 Offset 0x720

Type R/W, reset 0x0000.0000



Bit/Field	Name	Туре	Reset	Description
31:6	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
5	S5	R/W	0	 I²C Module 5 Sleep Mode Clock Gating Control Value Description Enable and provide a clock to I²C module 5 in sleep mode. I²C module 5 is disabled.
4	S4	R/W	0	I ² C Module 4 Sleep Mode Clock Gating Control

- 1 Enable and provide a clock to I²C module 4 in sleep mode.
- 0 I²C module 4 is disabled.

Bit/Field	Name	Туре	Reset	Description
3	S3	R/W	0	I ² C Module 3 Sleep Mode Clock Gating Control
				Value Description 1 Enable and provide a clock to I ² C module 3 in sleep mode. 0 I ² C module 3 is disabled.
2	S2	R/W	0	I ² C Module 2 Sleep Mode Clock Gating Control Value Description 1 Enable and provide a clock to I ² C module 2 in sleep mode. 0 I ² C module 2 is disabled.
1	S1	R/W	0	I ² C Module 1 Sleep Mode Clock Gating Control Value Description 1 Enable and provide a clock to I ² C module 1 in sleep mode. 0 I ² C module 1 is disabled.
0	S0	R/W	0	I ² C Module 0 Sleep Mode Clock Gating Control Value Description 1 Enable and provide a clock to I ² C module 0 in sleep mode. 0 I ² C module 0 is disabled.

February 20, 2013 363

Register 75: Universal Serial Bus Sleep Mode Clock Gating Control (SCGCUSB), offset 0x728


The SCGCUSB register provides software the capability to enable and disable the USB module in sleep mode. When enabled, a module is provided a clock. When disabled, the clock is disabled to save power. This register provides the same capability as the legacy Sleep Mode Clock Gating Control Register n SCGCn registers specifically for the watchdog modules and has the same bit polarity as the corresponding SCGCn bits.

Important: This register should be used to control the clocking for the USB module. To support legacy software, the SCGC2 register is available. A write to the USB0 bit in the SCGC2 register also writes the S0 bit in this register. If the USB0 bit is changed by writing to the SCGC2 register, it can be read back correctly with a read of the SCGC2 register. If software uses this register to control the clock for the USB module, the write causes proper operation, but the USB0 bit in the SCGC2 register does not reflect the value of the S0 bit. If software uses both legacy and peripheral-specific register accesses, the peripheral-specific registers must be accessed by read-modify-write operations that affect only peripherals that are not present in the legacy registers. In this manner, both the peripheral-specific and legacy registers have coherent information.

Universal Serial Bus Sleep Mode Clock Gating Control (SCGCUSB)

Base 0x400F.E000 Offset 0x728

Type R/W, reset 0x0000.0000



Bit/Field	Name	Type	Reset	Description
31:1	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
0	S0	R/W	0	USB Module Sleep Mode Clock Gating Control

- 1 Enable and provide a clock to the USB module in sleep mode.
- 0 USB module is disabled.


Register 76: Controller Area Network Sleep Mode Clock Gating Control (SCGCCAN), offset 0x734

The **SCGCCAN** register provides software the capability to enable and disable the CAN modules in sleep mode. When enabled, a module is provided a clock. When disabled, the clock is disabled to save power. This register provides the same capability as the legacy **Sleep Mode Clock Gating Control Register n SCGCn** registers specifically for the watchdog modules and has the same bit polarity as the corresponding **SCGCn** bits.

Important: This register should be used to control the clocking for the CAN modules. To support legacy software, the SCGC0 register is available. A write to the SCGC0 register also writes the corresponding bit in this register. Any bits that are changed by writing to the SCGC0 register can be read back correctly with a read of the SCGC0 register. If software uses this register to write a legacy peripheral (such as CAN0), the write causes proper operation, but the value of that bit is not reflected in the SCGC0 register. If software uses both legacy and peripheral-specific register accesses, the peripheral-specific registers must be accessed by read-modify-write operations that affect only peripherals that are not present in the legacy registers. In this manner, both the peripheral-specific and legacy registers have coherent information.

Controller Area Network Sleep Mode Clock Gating Control (SCGCCAN)

Base 0x400F.E000 Offset 0x734 Type R/W, reset 0x0000.0000



Bit/Field	Name	Туре	Reset	Description
31:2	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
1	S1	R/W	0	CAN Module 1 Sleep Mode Clock Gating Control Value Description Enable and provide a clock to CAN module 1 in sleep mode. CAN module 1 is disabled.
0	S0	R/W	0	CAN Module 0 Sleep Mode Clock Gating Control

- 1 Enable and provide a clock to CAN module 0 in sleep mode.
- 0 CAN module 0 is disabled.


Register 77: Analog-to-Digital Converter Sleep Mode Clock Gating Control (SCGCADC), offset 0x738

The **SCGCADC** register provides software the capability to enable and disable the ADC modules in sleep mode. When enabled, a module is provided a clock. When disabled, the clock is disabled to save power. This register provides the same capability as the legacy **Sleep Mode Clock Gating Control Register n SCGCn** registers specifically for the watchdog modules and has the same bit polarity as the corresponding **SCGCn** bits.

Important: This register should be used to control the clocking for the ADC modules. To support legacy software, the SCGC0 register is available. A write to the SCGC0 register also writes the corresponding bit in this register. Any bits that are changed by writing to the SCGC0 register can be read back correctly with a read of the SCGC0 register. If software uses this register to write a legacy peripheral (such as ADC0), the write causes proper operation, but the value of that bit is not reflected in the SCGC0 register. If software uses both legacy and peripheral-specific register accesses, the peripheral-specific registers must be accessed by read-modify-write operations that affect only peripherals that are not present in the legacy registers. In this manner, both the peripheral-specific and legacy registers have coherent information.

Analog-to-Digital Converter Sleep Mode Clock Gating Control (SCGCADC)

Base 0x400F.E000 Offset 0x738 Type R/W, reset 0x0000.0000



Bit/Field	Name	Type	Reset	Description
31:2	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
1	S1	R/W	0	ADC Module 1 Sleep Mode Clock Gating Control
				Value Description 1 Enable and provide a clock to ADC module 1 in sleep mode.
				0 ADC module 1 is disabled.
0	S0	R/W	0	ADC Module 0 Sleep Mode Clock Gating Control
				Value Description

Enable and provide a clock to ADC module 0 in sleep mode.

0 ADC module 0 is disabled.

Register 78: Analog Comparator Sleep Mode Clock Gating Control (SCGCACMP), offset 0x73C


The **SCGCACMP** register provides software the capability to enable and disable the analog comparator module in sleep mode. When enabled, a module is provided a clock. When disabled, the clock is disabled to save power. This register provides the same capability as the legacy Sleep Mode Clock Gating Control Register n SCGCn registers specifically for the watchdog modules and has the same bit polarity as the corresponding SCGCn bits.

Important: This register should be used to control the clocking for the analog comparator module. To support legacy software, the SCGC1 register is available. Setting any of the COMPn bits in the SCGC1 register also sets the S0 bit in this register. If any of the COMPn bits are set by writing to the SCGC1 register, it can be read back correctly when reading the SCGC1 register. If software uses this register to change the clocking for the analog comparator module, the write causes proper operation, but the value S0 is not reflected by the COMPn bits in the SCGC1 register. If software uses both legacy and peripheral-specific register accesses, the peripheral-specific registers must be accessed by read-modify-write operations that affect only peripherals that are not present in the legacy registers. In this manner, both the peripheral-specific and legacy registers have coherent information.

Analog Comparator Sleep Mode Clock Gating Control (SCGCACMP)

Base 0x400F.E000 Offset 0x73C

Type R/W, reset 0x0000.0000



Bit/Field	Name	Туре	Reset	Description
31:1	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
0	SO	R/M	Λ	Analog Comparator Module O Sleep Mode Clock Gating Control

- 1 Enable and provide a clock to the analog comparator module in sleep mode.
- 0 Analog comparator module is disabled.

Register 79: Pulse Width Modulator Sleep Mode Clock Gating Control (SCGCPWM), offset 0x740

The **SCGCPWM** register provides software the capability to enable and disable the PWM modules in sleep mode. When enabled, a module is provided a clock. When disabled, the clock is disabled to save power. This register provides the same capability as the legacy **Sleep Mode Clock Gating Control Register n SCGCn** registers specifically for the watchdog modules and has the same bit polarity as the corresponding **SCGCn** bits.


Important: This register should be used to control the clocking for the PWM modules. To support legacy software, the SCGC0 register is available. A write to the PWM bit in the SCGC0 register also writes the S0 bit in this register. If the PWM bit is changed by writing to the SCGC0 register, it can be read back correctly with a read of the SCGC0 register. Software must use this register to support modules that are not present in the legacy registers. If software uses this register to write to S0, the write causes proper operation.

registers. If software uses this register to write to S0, the write causes proper operation, but the value of that bit is not reflected in the PWM bit in the **SCGC0** register. If software uses both legacy and peripheral-specific register accesses, the peripheral-specific registers must be accessed by read-modify-write operations that affect only peripherals that are not present in the legacy registers. In this manner, both the peripheral-specific and legacy registers have coherent information.

Pulse Width Modulator Sleep Mode Clock Gating Control (SCGCPWM)

Base 0x400F.E000 Offset 0x740

Type R/W, reset 0x0000.0000



Bit/Field	Name	Туре	Reset	Description
31:2	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
1	S1	R/W	0	PWM Module 1 Sleep Mode Clock Gating Control
				Value Description 1 Enable and provide a clock to PWM module 1 in sleep mode. 0 PWM module 1 is disabled.
0	S0	R/W	0	PWM Module 0 Sleep Mode Clock Gating Control

- 1 Enable and provide a clock to PWM module 0 in sleep mode.
- 0 PWM module 0 is disabled.


Register 80: Quadrature Encoder Interface Sleep Mode Clock Gating Control (SCGCQEI), offset 0x744

The **SCGCQEI** register provides software the capability to enable and disable the QEI modules in sleep mode. When enabled, a module is provided a clock. When disabled, the clock is disabled to save power. This register provides the same capability as the legacy **Sleep Mode Clock Gating Control Register n SCGCn** registers specifically for the watchdog modules and has the same bit polarity as the corresponding **SCGCn** bits.

Important: This register should be used to control the clocking for the QEI modules. To support legacy software, the SCGC1 register is available. A write to the SCGC1 register also writes the corresponding bit in this register. Any bits that are changed by writing to the SCGC1 register can be read back correctly with a read of the SCGC1 register. If software uses this register to write a legacy peripheral (such as QEI0), the write causes proper operation, but the value of that bit is not reflected in the SCGC1 register. If software uses both legacy and peripheral-specific register accesses, the peripheral-specific registers must be accessed by read-modify-write operations that affect only peripherals that are not present in the legacy registers. In this manner, both the peripheral-specific and legacy registers have coherent information.

Quadrature Encoder Interface Sleep Mode Clock Gating Control (SCGCQEI)

Base 0x400F.E000 Offset 0x744 Type R/W, reset 0x0000.0000



Bit/Field	Name	Туре	Reset	Description
31:2	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
1	S1	R/W	0	QEI Module 1 Sleep Mode Clock Gating Control Value Description 1 Enable and provide a clock to QEI module 1 in sleep mode. 0 QEI module 1 is disabled.
0	S0	R/W	0	QEI Module 0 Sleep Mode Clock Gating Control Value Description

1

0

Enable and provide a clock to QEI module 0 in sleep mode.

QEI module 0 is disabled.


Register 81: EEPROM Sleep Mode Clock Gating Control (SCGCEEPROM), offset 0x758

The **SCGCEEPROM** register provides software the capability to enable and disable the EEPROM module in sleep mode. When enabled, a module is provided a clock. When disabled, the clock is disabled to save power.

EEPROM Sleep Mode Clock Gating Control (SCGCEEPROM)

Base 0x400F.E000

Offset 0x758
Type R/W, reset 0x0000.0000



Bit/Field	Name	Туре	Reset	Description
31:1	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
0	S0	R/W	0	EEPROM Module Sleep Mode Clock Gating Control

- Enable and provide a clock to the EEPROM module in sleep mode.
- 0 EEPROM module is disabled.


Register 82: 32/64-Bit Wide General-Purpose Timer Sleep Mode Clock Gating Control (SCGCWTIMER), offset 0x75C

The SCGCWTIMER register provides software the capability to enable and disable 3264-bit timer modules in sleep mode. When enabled, a module is provided a clock. When disabled, the clock is disabled to save power. This register provides the same capability as the legacy Sleep Mode Clock Gating Control Register n SCGCn registers specifically for the timer modules and has the same bit polarity as the corresponding SCGCn bits.

32/64-Bit Wide General-Purpose Timer Sleep Mode Clock Gating Control (SCGCWTIMER)

Base 0x400F.E000

Offset 0x75C Type R/W, reset 0x0000.0000



Bit/Field	Name	Type	Reset	Description
31:6	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
5	S5	R/W	0	32/64-Bit Wide General-Purpose Timer 5 Sleep Mode Clock Gating Control
				Value Description
				1 Enable and provide a clock to 32/64-bit wide general-purpose timer module 5 in sleep mode.
				0 32/64-bit wide general-purpose timer module 5 is disabled.
4	S4	R/W	0	32/64-Bit Wide General-Purpose Timer 4 Sleep Mode Clock Gating Control
				Value Description
				1 Enable and provide a clock to 32/64-bit wide general-purpose timer module 4 in sleep mode.
				0 32/64-bit wide general-purpose timer module 4 is disabled.
3	\$3	R/W	0	32/64-Bit Wide General-Purpose Timer 3 Sleep Mode Clock Gating Control
				Value Description

- Enable and provide a clock to 32/64-bit wide general-purpose timer module 3 in sleep mode.
- 0 32/64-bit wide general-purpose timer module 3 is disabled.

Bit/Field	Name	Туре	Reset	Description
2	S2	R/W	0	32/64-Bit Wide General-Purpose Timer 2 Sleep Mode Clock Gating Control
				Value Description
				1 Enable and provide a clock to 32/64-bit wide general-purpose timer module 2 in sleep mode.
				0 32/64-bit wide general-purpose timer module 2 is disabled.
1	S1	R/W	0	32/64-Bit Wide General-Purpose Timer 1 Sleep Mode Clock Gating Control
				Value Description
				1 Enable and provide a clock to 32/64-bit wide general-purpose timer module 1 in sleep mode.
				0 32/64-bit wide general-purpose timer module 1 is disabled.
0	S0	R/W	0	32/64-Bit Wide General-Purpose Timer 0 Sleep Mode Clock Gating Control
				Value Description
				1 Enable and provide a clock to 32/64-bit wide general-purpose timer module 0 in sleep mode.
				0 32/64-bit wide general-purpose timer module 0 is disabled.


Register 83: Watchdog Timer Deep-Sleep Mode Clock Gating Control (DCGCWD), offset 0x800

The **DCGCWD** register provides software the capability to enable and disable watchdog modules in deep-sleep mode. When enabled, a module is provided a clock. When disabled, the clock is disabled to save power. This register provides the same capability as the legacy **Deep-Sleep Mode Clock Gating Control Register n DCGCn** registers specifically for the watchdog modules and has the same bit polarity as the corresponding **DCGCn** bits.

Important: This register should be used to control the clocking for the watchdog modules. To support legacy software, the DCGC0 register is available. A write to the DCGC0 register also writes the corresponding bit in this register. Any bits that are changed by writing to the DCGC0 register can be read back correctly with a read of the DCGC0 register. If software uses this register to write a legacy peripheral (such as Watchdog 0), the write causes proper operation, but the value of that bit is not reflected in the DCGC0 register. If software uses both legacy and peripheral-specific register accesses, the peripheral-specific registers must be accessed by read-modify-write operations that affect only peripherals that are not present in the legacy registers. In this manner, both the peripheral-specific and legacy registers have coherent information.

Watchdog Timer Deep-Sleep Mode Clock Gating Control (DCGCWD)

Base 0x400F.E000 Offset 0x800 Type R/W, reset 0x0000.0000



Bit/Field	Name	Туре	Reset	Description
31:2	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
1	D1	R/W	0	Watchdog Timer 1 Deep-Sleep Mode Clock Gating Control
				Value Description
				Enable and provide a clock to Watchdog module 1 in deep-sleep mode.
				0 Watchdog module 1 is disabled.
0	D0	R/W	0	Watchdog Timer 0 Deep-Sleep Mode Clock Gating Control
				Value Description
				1 Enable and provide a clock to Watchdog module 0 in deep-sleep mode.

0

Watchdog module 0 is disabled.

Register 84: 16/32-Bit General-Purpose Timer Deep-Sleep Mode Clock Gating Control (DCGCTIMER), offset 0x804

The **DCGCTIMER** register provides software the capability to enable and disable 16/32-bit timer modules in deep-sleep mode. When enabled, a module is provided a clock. When disabled, the clock is disabled to save power. This register provides the same capability as the legacy **Deep-Sleep Mode Clock Gating Control Register n DCGCn** registers specifically for the timer modules and has the same bit polarity as the corresponding **DCGCn** bits.


Important: This register should be used to control the clocking for the timer modules. To support legacy software, the DCGC1 register is available. A write to the DCGC1 register also writes the corresponding bit in this register. Any bits that are changed by writing to the DCGC1 register can be read back correctly with a read of the DCGC1 register. Software must use this register to support modules that are not present in the legacy registers. If software uses this register to write a legacy peripheral (such as Timer 0), the write causes proper operation, but the value of that bit is not reflected in the DCGC1 register. If software uses both legacy and peripheral-specific register accesses, the peripheral-specific registers must be accessed by read-modify-write operations that affect only peripherals that are not present in the legacy registers. In this manner, both

the peripheral-specific and legacy registers have coherent information.

16/32-Bit General-Purpose Timer Deep-Sleep Mode Clock Gating Control (DCGCTIMER)

Base 0x400F.E000 Offset 0x804

Type R/W, reset 0x0000.0000



Bit/Field	Name	туре	Reset	Description
31:6	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
5	D5	R/W	0	16/32-Bit General-Purpose Timer 5 Deep-Sleep Mode Clock Gating Control

- Enable and provide a clock to 16/32-bit general-purpose timer module 5 in deep-sleep mode.
- 0 16/32-bit general-purpose timer module 5 is disabled.

Bit/Field	Name	Туре	Reset	Description
4	D4	R/W	0	16/32-Bit General-Purpose Timer 4 Deep-Sleep Mode Clock Gating Control
				Value Description
				1 Enable and provide a clock to 16/32-bit general-purpose timer module 4 in deep-sleep mode.
				0 16/32-bit general-purpose timer module 4 is disabled.
3	D3	R/W	0	16/32-Bit General-Purpose Timer 3 Deep-Sleep Mode Clock Gating Control
				Value Description
				Enable and provide a clock to 16/32-bit general-purpose timer module 3 in deep-sleep mode.
				0 16/32-bit general-purpose timer module 3 is disabled.
2	D2	R/W	0	16/32-Bit General-Purpose Timer 2 Deep-Sleep Mode Clock Gating Control
				Value Description
				Enable and provide a clock to 16/32-bit general-purpose timer module 2 in deep-sleep mode.
				0 16/32-bit general-purpose timer module 2 is disabled.
1	D1	R/W	0	16/32-Bit General-Purpose Timer 1 Deep-Sleep Mode Clock Gating Control
				Value Description
				Enable and provide a clock to 16/32-bit general-purpose timer module 1 in deep-sleep mode.
				0 16/32-bit general-purpose timer module 1 is disabled.
0	D0	R/W	0	16/32-Bit General-Purpose Timer 0 Deep-Sleep Mode Clock Gating Control
				Value Description
				1 Enable and provide a clock to 16/32-bit general-purpose timer module 0 in deep-sleep mode.
				0 16/32-bit general-purpose timer module 0 is disabled.

February 20, 2013 375

Register 85: General-Purpose Input/Output Deep-Sleep Mode Clock Gating Control (DCGCGPIO), offset 0x808


The **DCGCGPIO** register provides software the capability to enable and disable GPIO modules in deep-sleep mode. When enabled, a module is provided a clock. When disabled, the clock is disabled to save power. This register provides the same capability as the legacy **Deep-Sleep Mode Clock Gating Control Register n DCGCn** registers specifically for the watchdog modules and has the same bit polarity as the corresponding **DCGCn** bits.

Important: This register should be used to control the clocking for the GPIO modules. To support legacy software, the DCGC2 register is available. A write to the DCGC2 register also writes the corresponding bit in this register. Any bits that are changed by writing to the DCGC2 register can be read back correctly with a read of the DCGC2 register. Software must use this register to support modules that are not present in the legacy registers. If software uses this register to write a legacy peripheral (such as GPIO A), the write causes proper operation, but the value of that bit is not reflected in the DCGC2 register. If software uses both legacy and peripheral-specific register accesses, the peripheral-specific registers must be accessed by read-modify-write operations that affect only peripherals that are not present in the legacy registers. In this manner, both the peripheral-specific and legacy registers have coherent information.

General-Purpose Input/Output Deep-Sleep Mode Clock Gating Control (DCGCGPIO)

Base 0x400F.E000 Offset 0x808

Type R/W, reset 0x0000.0000



Bit/Field	Name	Type	Reset	Description
31:10	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
9	D9	R/W	0	 GPIO Port K Deep-Sleep Mode Clock Gating Control Value Description 1 Enable and provide a clock to GPIO Port K in deep-sleep mode. 0 GPIO Port K is disabled.
8	D8	R/W	0	GPIO Port J Deep-Sleep Mode Clock Gating Control

- 1 Enable and provide a clock to GPIO Port J in deep-sleep mode.
- 0 GPIO Port J is disabled.

Bit/Field	Name	Туре	Reset	Description
7	D7	R/W	0	GPIO Port H Deep-Sleep Mode Clock Gating Control
				Value Description 1 Enable and provide a clock to GPIO Port H in deep-sleep mode.
				0 GPIO Port H is disabled.
6	D6	R/W	0	GPIO Port G Deep-Sleep Mode Clock Gating Control
				Value Description
				1 Enable and provide a clock to GPIO Port G in deep-sleep mode.
				0 GPIO Port G is disabled.
5	D5	R/W	0	GPIO Port F Deep-Sleep Mode Clock Gating Control
				Value Description
				1 Enable and provide a clock to GPIO Port F in deep-sleep mode.
				0 GPIO Port F is disabled.
4	D4	R/W	0	GPIO Port E Deep-Sleep Mode Clock Gating Control
				Value Description
				1 Enable and provide a clock to GPIO Port E in deep-sleep mode.
				0 GPIO Port E is disabled.
3	D3	R/W	0	GPIO Port D Deep-Sleep Mode Clock Gating Control
				Value Description
				1 Enable and provide a clock to GPIO Port D in deep-sleep mode.
				0 GPIO Port D is disabled.
2	D2	R/W	0	GPIO Port C Deep-Sleep Mode Clock Gating Control
				Value Description
				1 Enable and provide a clock to GPIO Port C in deep-sleep mode.
				0 GPIO Port C is disabled.
1	D1	R/W	0	GPIO Port B Deep-Sleep Mode Clock Gating Control
				Value Description
				1 Enable and provide a clock to GPIO Port B in deep-sleep mode.
				0 GPIO Port B is disabled.

February 20, 2013 377

Bit/Field	Name	Туре	Reset	Description
0	D0	R/W	0	GPIO Port A Deep-Sleep Mode Clock Gating Control
				Value Description
				1 Enable and provide a clock to GPIO Port A in deep-sleep mode.
				0 GPIO Port A is disabled.

Register 86: Micro Direct Memory Access Deep-Sleep Mode Clock Gating Control (DCGCDMA), offset 0x80C


The **DCGCDMA** register provides software the capability to enable and disable the uDMA module in deep-sleep mode. When enabled, a module is provided a clock. When disabled, the clock is disabled to save power. This register provides the same capability as the legacy Deep-Sleep Mode Clock Gating Control Register n DCGCn registers specifically for the watchdog modules and has the same bit polarity as the corresponding **DCGCn** bits.

Important: This register should be used to control the clocking for the µDMA module. To support legacy software, the DCGC2 register is available. A write to the UDMA bit in the DCGC2 register also writes the D0 bit in this register. If the UDMA bit is changed by writing to the DCGC2 register, it can be read back correctly with a read of the DCGC2 register. If software uses this register to control the clock for the µDMA module, the write causes proper operation, but the UDMA bit in the DCGC2 register does not reflect the value of the D0 bit. If software uses both legacy and peripheral-specific register accesses, the peripheral-specific registers must be accessed by read-modify-write operations that affect only peripherals that are not present in the legacy registers. In this manner, both the peripheral-specific and legacy registers have coherent information.

Micro Direct Memory Access Deep-Sleep Mode Clock Gating Control (DCGCDMA)

Base 0x400F.E000 Offset 0x80C

Type R/W, reset 0x0000.0000



Bit/Field	Name	Type	Reset	Description
31:1	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
0	D0	R/W	0	μDMA Module Deep-Sleep Mode Clock Gating Control

- 1 Enable and provide a clock to the µDMA module in deep-sleep mode.
- 0 μDMA module is disabled.

Register 87: Hibernation Deep-Sleep Mode Clock Gating Control (DCGCHIB), offset 0x814


The **DCGCHIB** register provides software the capability to enable and disable the Hibernation module in deep-sleep mode. When enabled, a module is provided a clock. When disabled, the clock is disabled to save power. This register provides the same capability as the legacy **Deep-Sleep Mode Clock Gating Control Register n DCGCn** registers specifically for the watchdog modules and has the same bit polarity as the corresponding **DCGCn** bits.

Important: This register should be used to control the clocking for the Hibernation module. To support legacy software, the DCGC0 register is available. A write to the HIB bit in the DCGC0 register also writes the D0 bit in this register. If the HIB bit is changed by writing to the DCGC0 register, it can be read back correctly with a read of the DCGC0 register. If software uses this register to control the clock for the Hibernation module, the write causes proper operation, but the HIB bit in the DCGC0 register does not reflect the value of the D0 bit. If software uses both legacy and peripheral-specific register accesses, the peripheral-specific registers must be accessed by read-modify-write operations that affect only peripherals that are not present in the legacy registers. In this manner, both the peripheral-specific and legacy registers have coherent information.

Hibernation Deep-Sleep Mode Clock Gating Control (DCGCHIB)

Base 0x400F.E000 Offset 0x814

Type R/W, reset 0x0000.0001



Bit/Field	Name	Type	Reset	Description
31:1	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
0	D0	R/W	1	Hibernation Module Deep-Sleep Mode Clock Gating Control

- Enable and provide a clock to the Hibernation module in deep-sleep mode.
- 0 Hibernation module is disabled.

Register 88: Universal Asynchronous Receiver/Transmitter Deep-Sleep Mode Clock Gating Control (DCGCUART), offset 0x818


The **DCGCUART** register provides software the capability to enable and disable the UART modules in deep-sleep mode. When enabled, a module is provided a clock. When disabled, the clock is disabled to save power. This register provides the same capability as the legacy **Deep-Sleep Mode Clock Gating Control Register n DCGCn** registers specifically for the watchdog modules and has the same bit polarity as the corresponding **DCGCn** bits.

Important: This register should be used to control the clocking for the UART modules. To support legacy software, the DCGC1 register is available. A write to the DCGC1 register also writes the corresponding bit in this register. Any bits that are changed by writing to the DCGC1 register can be read back correctly with a read of the DCGC1 register. Software must use this register to support modules that are not present in the legacy registers. If software uses this register to write a legacy peripheral (such as UART0), the write causes proper operation, but the value of that bit is not reflected in the DCGC1 register. If software uses both legacy and peripheral-specific register accesses, the peripheral-specific registers must be accessed by read-modify-write operations that affect only peripherals that are not present in the legacy registers. In this manner, both the peripheral-specific and legacy registers have coherent information.

Universal Asynchronous Receiver/Transmitter Deep-Sleep Mode Clock Gating Control (DCGCUART)

Base 0x400F.E000 Offset 0x818

Type R/W, reset 0x0000.0000



Bit/Field	Name	Туре	Reset	Description
31:8	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
7	D7	R/W	0	UART Module 7 Deep-Sleep Mode Clock Gating Control
				Value Description
				Enable and provide a clock to UART module 7 in deep-sleep mode.
				0 UART module 7 is disabled.
6	D6	R/W	0	UART Module 6 Deep-Sleep Mode Clock Gating Control
				Value Description
				Enable and provide a clock to UART module 6 in deep-sleep mode.
				0 UART module 6 is disabled.

Bit/Field	Name	Туре	Reset	Description
5	D5	R/W	0	UART Module 5 Deep-Sleep Mode Clock Gating Control
				Value Description
				 Enable and provide a clock to UART module 5 in deep-sleep mode.
				0 UART module 5 is disabled.
4	D4	R/W	0	UART Module 4 Deep-Sleep Mode Clock Gating Control
				Value Description
				 Enable and provide a clock to UART module 4 in deep-sleep mode.
				0 UART module 4 is disabled.
3	D3	R/W	0	UART Module 3 Deep-Sleep Mode Clock Gating Control
				Value Description
				1 Enable and provide a clock to UART module 3 in deep-sleep mode.
				0 UART module 3 is disabled.
2	D2	R/W	0	UART Module 2 Deep-Sleep Mode Clock Gating Control
				Value Description
				1 Enable and provide a clock to UART module 2 in deep-sleep mode.
				0 UART module 2 is disabled.
1	D1	R/W	0	UART Module 1 Deep-Sleep Mode Clock Gating Control
				Value Description
				Enable and provide a clock to UART module 1 in deep-sleep mode.
				0 UART module 1 is disabled.
0	D0	R/W	0	UART Module 0 Deep-Sleep Mode Clock Gating Control
				Value Description
				Enable and provide a clock to UART module 0 in deep-sleep mode.
				0 UART module 0 is disabled.

Register 89: Synchronous Serial Interface Deep-Sleep Mode Clock Gating Control (DCGCSSI), offset 0x81C


The **DCGCSSI** register provides software the capability to enable and disable the SSI modules in deep-sleep mode. When enabled, a module is provided a clock. When disabled, the clock is disabled to save power. This register provides the same capability as the legacy **Deep-Sleep Mode Clock Gating Control Register n DCGCn** registers specifically for the watchdog modules and has the same bit polarity as the corresponding **DCGCn** bits.

Important: This register should be used to control the clocking for the SSI modules. To support legacy software, the DCGC1 register is available. A write to the DCGC1 register also writes the corresponding bit in this register. Any bits that are changed by writing to the DCGC1 register can be read back correctly with a read of the DCGC1 register. Software must use this register to support modules that are not present in the legacy registers. If software uses this register to write a legacy peripheral (such as SSI0), the write causes proper operation, but the value of that bit is not reflected in the DCGC1 register. If software uses both legacy and peripheral-specific register accesses, the peripheral-specific registers must be accessed by read-modify-write operations that affect only peripherals that are not present in the legacy registers. In this manner, both the peripheral-specific and legacy registers have coherent information.

Synchronous Serial Interface Deep-Sleep Mode Clock Gating Control (DCGCSSI)

Base 0x400F.E000 Offset 0x81C

Type R/W, reset 0x0000.0000



Bit/Field	Name	Туре	Reset	Description
31:4	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
3	D3	R/W	0	SSI Module 3 Deep-Sleep Mode Clock Gating Control Value Description
				Enable and provide a clock to SSI module 3 in deep-sleep mode.
				0 SSI module 3 is disabled.
2	D2	R/W	0	SSI Module 2 Deep-Sleep Mode Clock Gating Control

- 1 Enable and provide a clock to SSI module 2 in deep-sleep mode.
- 0 SSI module 2 is disabled.

Bit/Field	Name	Type	Reset	Description
1	D1	R/W	0	SSI Module 1 Deep-Sleep Mode Clock Gating Control
				Value Description 1 Enable and provide a clock to SSI module 1 in deep-sleep mode. 0 SSI module 1 is disabled.
0	D0	R/W	0	SSI Module 0 Deep-Sleep Mode Clock Gating Control Value Description 1 Enable and provide a clock to SSI module 0 in deep-sleep mode. 0 SSI module 0 is disabled.

Register 90: Inter-Integrated Circuit Deep-Sleep Mode Clock Gating Control (DCGCI2C), offset 0x820


The **DCGCI2C** register provides software the capability to enable and disable the I²C modules in deep-sleep mode. When enabled, a module is provided a clock. When disabled, the clock is disabled to save power. This register provides the same capability as the legacy **Deep-Sleep Mode Clock Gating Control Register n DCGCn** registers specifically for the watchdog modules and has the same bit polarity as the corresponding **DCGCn** bits.

Important: This register should be used to control the clocking for the I²C modules. To support legacy software, the DCGC1 register is available. A write to the DCGC1 register also writes the corresponding bit in this register. Any bits that are changed by writing to the DCGC1 register can be read back correctly with a read of the DCGC1 register. Software must use this register to support modules that are not present in the legacy registers. If software uses this register to write a legacy peripheral (such as I²CO), the write causes proper operation, but the value of that bit is not reflected in the DCGC1 register. If software uses both legacy and peripheral-specific register accesses, the peripheral-specific registers must be accessed by read-modify-write operations that affect only peripherals that are not present in the legacy registers. In this manner, both the peripheral-specific and legacy registers have coherent information.

Inter-Integrated Circuit Deep-Sleep Mode Clock Gating Control (DCGCI2C)

Base 0x400F.E000 Offset 0x820

Type R/W, reset 0x0000.0000



Bit/Field	Name	Туре	Reset	Description
31:6	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
5	D5	R/W	0	 I²C Module 5 Deep-Sleep Mode Clock Gating Control Value Description Enable and provide a clock to I²C module 5 in deep-sleep mode. I²C module 5 is disabled.
4	D4	R/W	0	I ² C Module 4 Deep-Sleep Mode Clock Gating Control

- 1 Enable and provide a clock to I²C module 4 in deep-sleep mode.
- 0 I²C module 4 is disabled.

Bit/Field	Name	Туре	Reset	Description				
3	D3	R/W	0	I ² C Module 3 Deep-Sleep Mode Clock Gating Control				
				Value Description 1 Enable and provide a clock to I ² C module 3 in deep-sleep mode. 0 I ² C module 3 is disabled.				
2	D2	R/W	0	I ² C Module 2 Deep-Sleep Mode Clock Gating Control				
				Value Description				
				1 Enable and provide a clock to I ² C module 2 in deep-sleep mode.				
				0 I ² C module 2 is disabled.				
1	D1	R/W	0	I ² C Module 1 Deep-Sleep Mode Clock Gating Control				
				Value Description				
				1 Enable and provide a clock to I ² C module 1 in deep-sleep mode.				
				0 I ² C module 1 is disabled.				
0	D0	R/W	0	I ² C Module 0 Deep-Sleep Mode Clock Gating Control				
				Value Description				
				1 Enable and provide a clock to I ² C module 0 in deep-sleep mode.				
				0 I ² C module 0 is disabled.				

Register 91: Universal Serial Bus Deep-Sleep Mode Clock Gating Control (DCGCUSB), offset 0x828


The **DCGCUSB** register provides software the capability to enable and disable the USB module in deep-sleep mode. When enabled, a module is provided a clock. When disabled, the clock is disabled to save power. This register provides the same capability as the legacy **Deep-Sleep Mode Clock Gating Control Register n DCGCn** registers specifically for the watchdog modules and has the same bit polarity as the corresponding **DCGCn** bits.

Important: This register should be used to control the clocking for the USB module. To support legacy software, the DCGC2 register is available. A write to the USB0 bit in the DCGC2 register also writes the D0 bit in this register. If the USB0 bit is changed by writing to the DCGC2 register, it can be read back correctly with a read of the DCGC2 register. If software uses this register to control the clock for the USB module, the write causes proper operation, but the USB0 bit in the DCGC2 register does not reflect the value of the D0 bit. If software uses both legacy and peripheral-specific register accesses, the peripheral-specific registers must be accessed by read-modify-write operations that affect only peripherals that are not present in the legacy registers. In this manner, both the peripheral-specific and legacy registers have coherent information.

Universal Serial Bus Deep-Sleep Mode Clock Gating Control (DCGCUSB)

Base 0x400F.E000 Offset 0x828

Type R/W, reset 0x0000.0000



Bit/Field	Name	Type	Reset	Description
31:1	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
0	D0	R/W	0	USB Module Deep-Sleep Mode Clock Gating Control

- Enable and provide a clock to the USB module in deep-sleep mode.
- 0 USB module is disabled.

Register 92: Controller Area Network Deep-Sleep Mode Clock Gating Control (DCGCCAN), offset 0x834

The **DCGCCAN** register provides software the capability to enable and disable the CAN modules in deep-sleep mode. When enabled, a module is provided a clock. When disabled, the clock is disabled to save power. This register provides the same capability as the legacy **Deep-Sleep Mode Clock Gating Control Register n DCGCn** registers specifically for the watchdog modules and has the same bit polarity as the corresponding **DCGCn** bits.

Important: This register should be used to control the clocking for the CAN modules. To support legacy software, the DCGC0 register is available. A write to the DCGC0 register also writes the corresponding bit in this register. Any bits that are changed by writing to the DCGC0 register can be read back correctly with a read of the DCGC0 register. If software uses this register to write a legacy peripheral (such as CAN0), the write causes proper operation, but the value of that bit is not reflected in the DCGC0 register. If software uses both legacy and peripheral-specific register accesses, the peripheral-specific registers must be accessed by read-modify-write operations that affect only peripherals that are not present in the legacy registers. In this manner, both the peripheral-specific and legacy registers have coherent information.

Controller Area Network Deep-Sleep Mode Clock Gating Control (DCGCCAN)

Base 0x400F.E000 Offset 0x834 Type R/W, reset 0x0000.0000

	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16
					·			rese	rved						1	
Type	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO
Reset	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0
	15	14	13	12	11	10	9	8	7	6	5	4	3	2	1	0
						reserved								D1	D0	
Type Reset	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	R/W 0	R/W 0

561 0 1	0 0	0 0	O	
Bit/Field	Name	Туре	Reset	Description
31:2	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
1	D1	R/W	0	CAN Module 1 Deep-Sleep Mode Clock Gating Control
				Value Description
				Enable and provide a clock to CAN module 1 in deep-sleep mode.
				0 CAN module 1 is disabled.
0	D0	R/W	0	CAN Module 0 Deep-Sleep Mode Clock Gating Control
				Value Description
				Enable and provide a clock to CAN module 0 in deep-sleep mode.
				0 CAN module 0 is disabled.


Register 93: Analog-to-Digital Converter Deep-Sleep Mode Clock Gating Control (DCGCADC), offset 0x838

The **DCGCADC** register provides software the capability to enable and disable the ADC modules in deep-sleep mode. When enabled, a module is provided a clock. When disabled, the clock is disabled to save power. This register provides the same capability as the legacy **Deep-Sleep Mode Clock Gating Control Register n DCGCn** registers specifically for the watchdog modules and has the same bit polarity as the corresponding **DCGCn** bits.

Important: This register should be used to control the clocking for the ADC modules. To support legacy software, the DCGC0 register is available. A write to the DCGC0 register also writes the corresponding bit in this register. Any bits that are changed by writing to the DCGC0 register can be read back correctly with a read of the DCGC0 register. If software uses this register to write a legacy peripheral (such as ADC0), the write causes proper operation, but the value of that bit is not reflected in the DCGC0 register. If software uses both legacy and peripheral-specific register accesses, the peripheral-specific registers must be accessed by read-modify-write operations that affect only peripherals that are not present in the legacy registers. In this manner, both the peripheral-specific and legacy registers have coherent information.

Analog-to-Digital Converter Deep-Sleep Mode Clock Gating Control (DCGCADC)

Base 0x400F.E000 Offset 0x838 Type R/W, reset 0x0000.0000



Bit/Field	Name	Туре	Reset	Description
31:2	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
1	D1	R/W	0	ADC Module 1 Deep-Sleep Mode Clock Gating Control
				Value Description
				Enable and provide a clock to ADC module 1 in deep-sleep mode.
				0 ADC module 1 is disabled.
0	D0	R/W	0	ADC Module 0 Deep-Sleep Mode Clock Gating Control
				Value Description
				Enable and provide a clock to ADC module 0 in deep-sleep mode.
				0 ADC module 0 is disabled.

Register 94: Analog Comparator Deep-Sleep Mode Clock Gating Control (DCGCACMP), offset 0x83C


The **DCGCACMP** register provides software the capability to enable and disable the analog comparator module in deep-sleep mode. When enabled, a module is provided a clock. When disabled, the clock is disabled to save power. This register provides the same capability as the legacy Deep-Sleep Mode Clock Gating Control Register n DCGCn registers specifically for the watchdog modules and has the same bit polarity as the corresponding **DCGCn** bits.

Important: This register should be used to control the clocking for the analog comparator module. To support legacy software, the **DCGC1** register is available. Setting any of the COMPn bits in the DCGC1 register also sets the D0 bit in this register. If any of the COMPn bits are set by writing to the DCGC1 register, it can be read back correctly when reading the **DCGC1** register. If software uses this register to change the clocking for the analog comparator module, the write causes proper operation, but the value D0 is not reflected by the COMPn bits in the DCGC1 register. If software uses both legacy and peripheral-specific register accesses, the peripheral-specific registers must be accessed by read-modify-write operations that affect only peripherals that are not present in the legacy registers. In this manner, both the peripheral-specific and legacy registers have coherent information.

Analog Comparator Deep-Sleep Mode Clock Gating Control (DCGCACMP)

Base 0x400F.E000 Offset 0x83C

Type R/W, reset 0x0000.0000



Bit/Field	Name	Type	Reset	Description
31:1	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
n	DO	DΛM	0	Analog Comparator Module O Deen-Sleen Mode Clock Gating Control

- 1 Enable and provide a clock to the analog comparator module in deep-sleep mode.
- 0 Analog comparator module is disabled.

Register 95: Pulse Width Modulator Deep-Sleep Mode Clock Gating Control (DCGCPWM), offset 0x840

The **DCGCPWM** register provides software the capability to enable and disable the PWM modules in deep-sleep mode. When enabled, a module is provided a clock. When disabled, the clock is disabled to save power. This register provides the same capability as the legacy **Deep-Sleep Mode Clock Gating Control Register n DCGCn** registers specifically for the watchdog modules and has the same bit polarity as the corresponding **DCGCn** bits.


Important: This register should be used to control the clocking for the PWM modules. To support legacy software, the DCGC0 register is available. A write to the PWM bit in the DCGC0 register also writes the D0 bit in this register. If the PWM bit is changed by writing to the DCGC0 register, it can be read back correctly with a read of the DCGC0 register. Software must use this register to support modules that are not present in the legacy registers. If software uses this register to write to D0, the write causes proper operation, but the value of that bit is not reflected in the PWM bit in the DCGC0 register. If software

uses both legacy and peripheral-specific register accesses, the peripheral-specific registers must be accessed by read-modify-write operations that affect only peripherals that are not present in the legacy registers. In this manner, both the peripheral-specific and legacy registers have coherent information.

Pulse Width Modulator Deep-Sleep Mode Clock Gating Control (DCGCPWM)

Base 0x400F.E000 Offset 0x840

Type R/W, reset 0x0000.0000



Bit/Field	Name	Туре	Reset	Description
31:2	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
1	D1	R/W	0	PWM Module 1 Deep-Sleep Mode Clock Gating Control
				Value Description
				Enable and provide a clock to PWM module 1 in deep-sleep mode.
				0 PWM module 1 is disabled.
0	D0	R/W	0	PWM Module 0 Deep-Sleep Mode Clock Gating Control
				Value Description
				Enable and provide a clock to PWM module 0 in deep-sleep mode.
				0 PWM module 0 is disabled.

Register 96: Quadrature Encoder Interface Deep-Sleep Mode Clock Gating Control (DCGCQEI), offset 0x844

The **DCGCQEI** register provides software the capability to enable and disable the QEI modules in deep-sleep mode. When enabled, a module is provided a clock. When disabled, the clock is disabled to save power. This register provides the same capability as the legacy **Deep-Sleep Mode Clock Gating Control Register n DCGCn** registers specifically for the watchdog modules and has the same bit polarity as the corresponding **DCGCn** bits.

Important: This register should be used to control the clocking for the QEI modules. To support legacy software, the DCGC1 register is available. A write to the DCGC1 register also writes the corresponding bit in this register. Any bits that are changed by writing to the DCGC1 register can be read back correctly with a read of the DCGC1 register. If software uses this register to write a legacy peripheral (such as QEI0), the write causes proper operation, but the value of that bit is not reflected in the DCGC1 register. If software uses both legacy and peripheral-specific register accesses, the peripheral-specific registers must be accessed by read-modify-write operations that affect only peripherals that are not present in the legacy registers. In this manner, both the peripheral-specific and legacy registers have coherent information.

Quadrature Encoder Interface Deep-Sleep Mode Clock Gating Control (DCGCQEI)

Base 0x400F.E000 Offset 0x844 Type R/W, reset 0x0000.0000

	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16
		1	1	1				rese	rved							
Type Reset	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0
	15	14	13	12	11	10	9	8	7	6	5	4	3	2	1	0
	reserved									D1	D0					
Type Reset	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	R/W 0	R/W 0

Bit/Field	Name	Type	Reset	Description
31:2	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
1	D1	R/W	0	QEI Module 1 Deep-Sleep Mode Clock Gating Control
				Value Description
				Enable and provide a clock to QEI module 1 in deep-sleep mode.
				0 QEI module 1 is disabled.
0	D0	R/W	0	QEI Module 0 Deep-Sleep Mode Clock Gating Control
				Value Description
				Enable and provide a clock to QEI module 0 in deep-sleep mode.
				0 QEI module 0 is disabled.


Register 97: EEPROM Deep-Sleep Mode Clock Gating Control (DCGCEEPROM), offset 0x858

The **DCGCEPROM** register provides software the capability to enable and disable the EEPROM module in deep-sleep mode. When enabled, a module is provided a clock. When disabled, the clock is disabled to save power.

EEPROM Deep-Sleep Mode Clock Gating Control (DCGCEEPROM)

Base 0x400F.E000 Offset 0x858

Type R/W, reset 0x0000.0000



Bit/Field	Name	Туре	Reset	Description
31:1	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
0	D0	R/W	0	EEPROM Module Deep-Sleep Mode Clock Gating Control

- 1 Enable and provide a clock to the EEPROM module in deep-sleep mode.
- 0 EEPROM module is disabled.


Register 98: 32/64-Bit Wide General-Purpose Timer Deep-Sleep Mode Clock Gating Control (DCGCWTIMER), offset 0x85C

The DCGCWTIMER register provides software the capability to enable and disable 32/64-bit wide timer modules in deep-sleep mode. When enabled, a module is provided a clock. When disabled, the clock is disabled to save power. This register provides the same capability as the legacy Deep-Sleep Mode Clock Gating Control Register n DCGCn registers specifically for the timer modules and has the same bit polarity as the corresponding **DCGCn** bits.

32/64-Bit Wide General-Purpose Timer Deep-Sleep Mode Clock Gating Control (DCGCWTIMER)

Base 0x400F.E000 Offset 0x85C

Type R/W, reset 0x0000.0000



Bit/Field	Name	Туре	Reset	Description			
31:6	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.			
5	D5	R/W	0	32/64-Bit Wide General-Purpose Timer 5 Deep-Sleep Mode Clock Gating Control			
				Value Description			
				1 Enable and provide a clock to 32/64-bit wide general-purpose timer module 5 in deep-sleep mode.			
				0 32/64-bit wide general-purpose timer module 5 is disabled.			
4	D4	R/W	0	32/64-Bit Wide General-Purpose Timer 4 Deep-Sleep Mode Clock Gating Control			
				Value Description			
				1 Enable and provide a clock to 32/64-bit wide general-purpose timer module 4 in deep-sleep mode.			
				0 32/64-bit wide general-purpose timer module 4 is disabled.			
3	D3	R/W	0	32/64-Bit Wide General-Purpose Timer 3 Deep-Sleep Mode Clock Gating Control			
				Value Description			

- Enable and provide a clock to 32/64-bit wide general-purpose timer module 3 in deep-sleep mode.
- 0 32/64-bit wide general-purpose timer module 3 is disabled.

Bit/Field	Name	Туре	Reset	Description
2	D2	R/W	0	32/64-Bit Wide General-Purpose Timer 2 Deep-Sleep Mode Clock Gating Control
				Value Description
				1 Enable and provide a clock to 32/64-bit wide general-purpose timer module 2 in deep-sleep mode.
				0 32/64-bit wide general-purpose timer module 2 is disabled.
1	D1	R/W	0	32/64-Bit Wide General-Purpose Timer 1 Deep-Sleep Mode Clock Gating Control
				Value Description
				1 Enable and provide a clock to 32/64-bit wide general-purpose timer module 1 in deep-sleep mode.
				0 32/64-bit wide general-purpose timer module 1 is disabled.
0	D0	R/W	0	32/64-Bit Wide General-Purpose Timer 0 Deep-Sleep Mode Clock Gating Control
				Value Description
				1 Enable and provide a clock to 32/64-bit wide general-purpose timer module 0 in deep-sleep mode.
				0 32/64-bit wide general-purpose timer module 0 is disabled.

Register 99: Watchdog Timer Peripheral Ready (PRWD), offset 0xA00


The **PRWD** register indicates whether the watchdog modules are ready to be accessed by software following a change in status of power, Run mode clocking, or reset. A Run mode clocking change is initiated if the corresponding **RCGCWD** bit is changed. A reset change is initiated if the corresponding **SRWD** bit is changed from 0 to 1.

The **PRWD** bit is cleared on any of the above events and is not set again until the module is completely powered, enabled, and internally reset.

Watchdog Timer Peripheral Ready (PRWD)

Base 0x400F.E000 Offset 0xA00

Type RO, reset 0x0000.0000



Bit/Field	Name	Type	Reset	Description
31:2	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
1	R1	RO	0	Watchdog Timer 1 Peripheral Ready
				Value Description
				1 Watchdog module 1 is ready for access.
				Watchdog module 1 is not ready for access. It is unclocked, unpowered, or in the process of completing a reset sequence.
0	R0	RO	0	Watchdog Timer 0 Peripheral Ready

- 1 Watchdog module 0 is ready for access.
- Watchdog module 0 is not ready for access. It is unclocked, unpowered, or in the process of completing a reset sequence.

Register 100: 16/32-Bit General-Purpose Timer Peripheral Ready (PRTIMER), offset 0xA04

The PRTIMER register indicates whether the timer modules are ready to be accessed by software following a change in status of power, Run mode clocking, or reset. A Run mode clocking change is initiated if the corresponding RCGCTIMER bit is changed. A reset change is initiated if the corresponding **SRTIMER** bit is changed from 0 to 1.

The PRTIMER bit is cleared on any of the above events and is not set again until the module is completely powered, enabled, and internally reset.

16/32-Bit General-Purpose Timer Peripheral Ready (PRTIMER)

Base 0x400F.E000 Offset 0xA04 Type RO, reset 0x0000.0000

	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16
								rese	rved							
Type	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO
Reset	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0
	15	14	13	12	11	10	9	8	7	6	5	4	3	2	1	0
					rese	rved		'			R5	R4	R3	R2	R1	R0
Type	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO
Reset	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0

Bit/Field	Name	Туре	Reset	Description
31:6	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
5	R5	RO	0	16/32-Bit General-Purpose Timer 5 Peripheral Ready
				Value Description
				1 16/32-bit timer module 5 is ready for access.
				0 16/32-bit timer module 5 is not ready for access. It is unclocked, unpowered, or in the process of completing a reset sequence.
4	R4	RO	0	16/32-Bit General-Purpose Timer 4 Peripheral Ready
				Value Description
				1 16/32-bit timer module 4 is ready for access.
				0 16/32-bit timer module 4 is not ready for access. It is unclocked, unpowered, or in the process of completing a reset sequence.
3	R3	RO	0	16/32-Bit General-Purpose Timer 3 Peripheral Ready
				Value Description

16/32-bit timer module 3 is ready for access.

0 16/32-bit timer module 3 is not ready for access. It is unclocked, unpowered, or in the process of completing a reset sequence.

1

Bit/Field	Name	Туре	Reset	Description
2	R2	RO	0	16/32-Bit General-Purpose Timer 2 Peripheral Ready
				Value Description
				1 16/32-bit timer module 2 is ready for access.
				0 16/32-bit timer module 2 is not ready for access. It is unclocked, unpowered, or in the process of completing a reset sequence.
1	R1	RO	0	16/32-Bit General-Purpose Timer 1 Peripheral Ready
				Value Description
				1 16/32-bit timer module 1 is ready for access.
				0 16/32-bit timer module 1 is not ready for access. It is unclocked, unpowered, or in the process of completing a reset sequence.
0	R0	RO	0	16/32-Bit General-Purpose Timer 0 Peripheral Ready
				Value Description
				1 16/32-bit timer module 0 is ready for access.
				0 16/32-bit timer module 0 is not ready for access. It is unclocked, unpowered, or in the process of completing a reset sequence.

Register 101: General-Purpose Input/Output Peripheral Ready (PRGPIO), offset 0xA08

The **PRGPIO** register indicates whether the GPIO modules are ready to be accessed by software following a change in status of power, Run mode clocking, or reset. A Run mode clocking change is initiated if the corresponding **RCGCGPIO** bit is changed. A reset change is initiated if the corresponding **SRGPIO** bit is changed from 0 to 1.

The **PRGPIO** bit is cleared on any of the above events and is not set again until the module is completely powered, enabled, and internally reset.

General-Purpose Input/Output Peripheral Ready (PRGPIO)

Base 0x400F.E000 Offset 0xA08 Type RO, reset 0x0000.0000

	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16
		•						rese	rved I							
Type	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO
Reset	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0
	15	14	13	12	11	10	9	8	7	6	5	4	3	2	1	0
		Î	rese	rved			R9	R8	R7	R6	R5	R4	R3	R2	R1	R0
Type .	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO
Reset	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0

Bit/Field	Name	Туре	Reset	Description
31:10	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
9	R9	RO	0	GPIO Port K Peripheral Ready
				Value Description
				1 GPIO Port K is ready for access.
				O GPIO Port K is not ready for access. It is unclocked, unpowered, or in the process of completing a reset sequence.
8	R8	RO	0	GPIO Port J Peripheral Ready
				Value Description
				1 GPIO Port J is ready for access.
				O GPIO Port J is not ready for access. It is unclocked, unpowered, or in the process of completing a reset sequence.
7	R7	RO	0	GPIO Port H Peripheral Ready

- 1 GPIO Port H is ready for access.
- 0 GPIO Port H is not ready for access. It is unclocked, unpowered, or in the process of completing a reset sequence.

Bit/Field	Name	Туре	Reset	Description
6	R6	RO	0	GPIO Port G Peripheral Ready
				Value Description
				1 GPIO Port G is ready for access.
				O GPIO Port G is not ready for access. It is unclocked, unpowered, or in the process of completing a reset sequence.
5	R5	RO	0	GPIO Port F Peripheral Ready
				Value Description
				1 GPIO Port F is ready for access.
				0 GPIO Port F is not ready for access. It is unclocked, unpowered, or in the process of completing a reset sequence.
4	R4	RO	0	GPIO Port E Peripheral Ready
				Value Description
				1 GPIO Port E is ready for access.
				O GPIO Port E is not ready for access. It is unclocked, unpowered, or in the process of completing a reset sequence.
3	R3	RO	0	GPIO Port D Peripheral Ready
				Value Description
				1 GPIO Port D is ready for access.
				0 GPIO Port D is not ready for access. It is unclocked, unpowered, or in the process of completing a reset sequence.
2	R2	RO	0	GPIO Port C Peripheral Ready
				Value Description
				1 GPIO Port C is ready for access.
				0 GPIO Port C is not ready for access. It is unclocked, unpowered, or in the process of completing a reset sequence.
1	R1	RO	0	GPIO Port B Peripheral Ready
				Value Description
				1 GPIO Port B is ready for access.
				0 GPIO Port B is not ready for access. It is unclocked, unpowered, or in the process of completing a reset sequence.
0	R0	RO	0	GPIO Port A Peripheral Ready
				Value Description
				1 GPIO Port A is ready for access.
				0 GPIO Port A is not ready for access. It is unclocked, unpowered, or in the process of completing a reset sequence.


Register 102: Micro Direct Memory Access Peripheral Ready (PRDMA), offset 0xA0C

The **PRDMA** register indicates whether the μ DMA module is ready to be accessed by software following a change in status of power, Run mode clocking, or reset. A Run mode clocking change is initiated if the corresponding **RCGCDMA** bit is changed. A reset change is initiated if the corresponding **SRDMA** bit is changed from 0 to 1.

The **PRDMA** bit is cleared on any of the above events and is not set again until the module is completely powered, enabled, and internally reset.

Micro Direct Memory Access Peripheral Ready (PRDMA)

Base 0x400F.E000 Offset 0xA0C Type RO, reset 0x0000.0000



Bit/Field	Name	Туре	Reset	Description
31:1	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
0	R0	RO	0	μDMA Module Peripheral Ready

- 1 The μDMA module is ready for access.
- The μDMA module is not ready for access. It is unclocked, unpowered, or in the process of completing a reset sequence.

Register 103: Hibernation Peripheral Ready (PRHIB), offset 0xA14


The **PRHIB** register indicates whether the Hibernation module is ready to be accessed by software following a change in status of power, Run mode clocking, or reset. A Run mode clocking change is initiated if the corresponding **RCGCHIB** bit is changed. A reset change is initiated if the corresponding **SRHIB** bit is changed from 0 to 1.

The **PRHIB** bit is cleared on any of the above events and is not set again until the module is completely powered, enabled, and internally reset.

Hibernation Peripheral Ready (PRHIB)

Base 0x400F.E000 Offset 0xA14

Type RO, reset 0x0000.0001



Bit/Field	Name	Type	Reset	Description
31:1	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
0	R0	RO	1	Hibernation Module Peripheral Ready

- 1 The Hibernation module is ready for access.
- The Hibernation module is not ready for access. It is unclocked, unpowered, or in the process of completing a reset sequence.

Register 104: Universal Asynchronous Receiver/Transmitter Peripheral Ready (PRUART), offset 0xA18

The **PRUART** register indicates whether the UART modules are ready to be accessed by software following a change in status of power, Run mode clocking, or reset. A Run mode clocking change is initiated if the corresponding **RCGCUART** bit is changed. A reset change is initiated if the corresponding **SRUART** bit is changed from 0 to 1.

The **PRUART** bit is cleared on any of the above events and is not set again until the module is completely powered, enabled, and internally reset.

Universal Asynchronous Receiver/Transmitter Peripheral Ready (PRUART)

Base 0x400F.E000 Offset 0xA18 Type RO, reset 0x0000.0000

	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16
		1	1					rese	rved I							
Type	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO
Reset	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0
									_		_					
	15	14	13	12	11	10	9	8	7	6	5	4	3	2	1	0
			'	rese	rved I			1	R7	R6	R5	R4	R3	R2	R1	R0
Туре	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO
Reset	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0

Bit/Field	Name	Туре	Reset	Description
31:8	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
7	R7	RO	0	UART Module 7 Peripheral Ready
				Value Description
				1 UART module 7 is ready for access.
				0 UART module 7 is not ready for access. It is unclocked, unpowered, or in the process of completing a reset sequence.
6	R6	RO	0	UART Module 6 Peripheral Ready
				Value Description
				1 UART module 6 is ready for access.
				0 UART module 6 is not ready for access. It is unclocked, unpowered, or in the process of completing a reset sequence.
5	R5	RO	0	UART Module 5 Peripheral Ready
				Value Description

1

UART module 5 is ready for access.

UART module 5 is not ready for access. It is unclocked, unpowered, or in the process of completing a reset sequence.

Bit/Field	Name	Туре	Reset	Description
4	R4	RO	0	UART Module 4 Peripheral Ready
				Value Description
				1 UART module 4 is ready for access.
				0 UART module 4 is not ready for access. It is unclocked, unpowered, or in the process of completing a reset sequence.
3	R3	RO	0	UART Module 3 Peripheral Ready
				Value Description
				1 UART module 3 is ready for access.
				0 UART module 3 is not ready for access. It is unclocked, unpowered, or in the process of completing a reset sequence.
2	R2	RO	0	UART Module 2 Peripheral Ready
				Value Description
				1 UART module 2 is ready for access.
				0 UART module 2 is not ready for access. It is unclocked, unpowered, or in the process of completing a reset sequence.
1	R1	RO	0	UART Module 1 Peripheral Ready
				Value Description
				1 UART module 1 is ready for access.
				UART module 1 is not ready for access. It is unclocked, unpowered, or in the process of completing a reset sequence.
0	R0	RO	0	UART Module 0 Peripheral Ready
				Value Description
				1 UART module 0 is ready for access.
				0 UART module 0 is not ready for access. It is unclocked, unpowered, or in the process of completing a reset sequence.

404 February 20, 2013

Register 105: Synchronous Serial Interface Peripheral Ready (PRSSI), offset 0xA1C

The PRSSI register indicates whether the SSI modules are ready to be accessed by software following a change in status of power, Run mode clocking, or reset. A Run mode clocking change is initiated if the corresponding RCGCSSI bit is changed. A reset change is initiated if the corresponding **SRSSI** bit is changed from 0 to 1.

The PRSSI bit is cleared on any of the above events and is not set again until the module is completely powered, enabled, and internally reset.

Synchronous Serial Interface Peripheral Ready (PRSSI)

Base 0x400F.E000 Offset 0xA1C Type RO, reset 0x0000.0000

	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16
		1	1					rese	rved I							
Type	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO
Reset	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0
	15	14	13	12	11	10	9	8	7	6	5	4	3	2	1	0
		ĺ	ı	1		rese	rved	l				ı	R3	R2	R1	R0
Type	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO
Reset	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0

Bit/Field	Name	Туре	Reset	Description
31:4	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
3	R3	RO	0	SSI Module 3 Peripheral Ready
				Value Description
				1 SSI module 3 is ready for access.
				O SSI module 3 is not ready for access. It is unclocked, unpowered, or in the process of completing a reset sequence.
2	R2	RO	0	SSI Module 2 Peripheral Ready
				Value Description
				1 SSI module 2 is ready for access.
				O SSI module 2 is not ready for access. It is unclocked, unpowered, or in the process of completing a reset sequence.
1	R1	RO	0	SSI Module 1 Peripheral Ready

- 1 SSI module 1 is ready for access.
- 0 SSI module 1 is not ready for access. It is unclocked, unpowered, or in the process of completing a reset sequence.

Bit/Field	Name	Type	Reset	Description
0	R0	RO	0	SSI Module 0 Peripheral Ready
				Value Description
				1 SSI module 0 is ready for access.
				O SSI module 0 is not ready for access. It is unclocked, unpowered, or in the process of completing a reset sequence.

Register 106: Inter-Integrated Circuit Peripheral Ready (PRI2C), offset 0xA20


The **PRI2C** register indicates whether the I²C modules are ready to be accessed by software following a change in status of power, Run mode clocking, or reset. A Run mode clocking change is initiated if the corresponding **RCGCI2C** bit is changed. A reset change is initiated if the corresponding **SRI2C** bit is changed from 0 to 1.

The **PRI2C** bit is cleared on any of the above events and is not set again until the module is completely powered, enabled, and internally reset.

Inter-Integrated Circuit Peripheral Ready (PRI2C)

Base 0x400F.E000 Offset 0xA20

Type RO, reset 0x0000.0000



Bit/Field	Name	Type	Reset	Description
31:6	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
5	R5	RO	0	I ² C Module 5 Peripheral Ready
				Value Description
				1 I ² C module 5 is ready for access.
				0 I ² C module 5 is not ready for access. It is unclocked, unpowered, or in the process of completing a reset sequence.
4	R4	RO	0	I ² C Module 4 Peripheral Ready
				Value Description
				1 I ² C module 4 is ready for access.
				0 I ² C module 4 is not ready for access. It is unclocked, unpowered, or in the process of completing a reset sequence.
3	R3	RO	0	I ² C Module 3 Peripheral Ready

- 1 I²C module 3 is ready for access.
- 0 I²C module 3 is not ready for access. It is unclocked, unpowered, or in the process of completing a reset sequence.

Bit/Field	Name	Туре	Reset	Description
2	R2	RO	0	I ² C Module 2 Peripheral Ready
				Value Description 1 I ² C module 2 is ready for access. 0 I ² C module 2 is not ready for access. It is unclocked, unpowered, or in the process of completing a reset sequence.
1	R1	RO	0	I ² C Module 1 Peripheral Ready Value Description 1 I ² C module 1 is ready for access. 0 I ² C module 1 is not ready for access. It is unclocked, unpowered, or in the process of completing a reset sequence.
0	R0	RO	0	 I²C Module 0 Peripheral Ready Value Description I²C module 0 is ready for access. I²C module 0 is not ready for access. It is unclocked, unpowered, or in the process of completing a reset sequence.

Register 107: Universal Serial Bus Peripheral Ready (PRUSB), offset 0xA28


The **PRUSB** register indicates whether the USB module is ready to be accessed by software following a change in Run mode clocking or reset. A Run mode clocking change is initiated if the corresponding **RCGCUSB** bit is changed. A reset change is initiated if the corresponding **SRUSB** bit is changed from 0 to 1.

The **PRUSB** bit is cleared on either of the above events and is not set again until the module is completely powered, enabled, and internally reset.

Universal Serial Bus Peripheral Ready (PRUSB)

Base 0x400F.E000 Offset 0xA28

Type RO, reset 0x0000.0000



Bit/Field	Name	Type	Reset	Description
31:1	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
0	R0	RO	0	USB Module Peripheral Ready

- 1 The USB module is ready for access.
- The USB module is not ready for access. It is unclocked, unpowered, or in the process of completing a reset sequence.

Register 108: Controller Area Network Peripheral Ready (PRCAN), offset 0xA34

The **PRCAN** register indicates whether the CAN modules are ready to be accessed by software following a change in status of power, Run mode clocking, or reset. A Run mode clocking change is initiated if the corresponding **RCGCCAN** bit is changed. A reset change is initiated if the corresponding **SRCAN** bit is changed from 0 to 1.

The **PRCAN** bit is cleared on any of the above events and is not set again until the module is completely powered, enabled, and internally reset.

Controller Area Network Peripheral Ready (PRCAN)

Base 0x400F.E000 Offset 0xA34 Type RO, reset 0x0000.0000

	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16
								rese	rved							
Type Reset	RO 0															
	15	14	13	12	11	10	9	8	7	6	5	4	3	2	1	0
							rese	rved							R1	R0
Type Reset	RO 0															

Bit/Field	Name	Туре	Reset	Description
31:2	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
1	R1	RO	0	CAN Module 1 Peripheral Ready
				Value Description
				1 CAN module 1 is ready for access.
				O CAN module 1 is not ready for access. It is unclocked, unpowered, or in the process of completing a reset sequence.
0	R0	RO	0	CAN Module 0 Peripheral Ready

- 1 CAN module 0 is ready for access.
- O CAN module 0 is not ready for access. It is unclocked, unpowered, or in the process of completing a reset sequence.

Register 109: Analog-to-Digital Converter Peripheral Ready (PRADC), offset 0xA38


The **PRADC** register indicates whether the ADC modules are ready to be accessed by software following a change in status of power, Run mode clocking, or reset. A Run mode clocking change is initiated if the corresponding **RCGCADC** bit is changed. A reset change is initiated if the corresponding **SRADC** bit is changed from 0 to 1.

The **PRADC** bit is cleared on any of the above events and is not set again until the module is completely powered, enabled, and internally reset.

Analog-to-Digital Converter Peripheral Ready (PRADC)

Base 0x400F.E000 Offset 0xA38

Type RO, reset 0x0000.0000



Bit/Field	Name	Туре	Reset	Description
31:2	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
1	R1	RO	0	ADC Module 1 Peripheral Ready
				Value Description
				1 ADC module 1 is ready for access.
				O ADC module 1 is not ready for access. It is unclocked, unpowered, or in the process of completing a reset sequence.
0	R0	RO	0	ADC Module 0 Peripheral Ready

- 1 ADC module 0 is ready for access.
- O ADC module 0 is not ready for access. It is unclocked, unpowered, or in the process of completing a reset sequence.

Register 110: Analog Comparator Peripheral Ready (PRACMP), offset 0xA3C


The **PRACMP** register indicates whether the analog comparator module is ready to be accessed by software following a change in status of power, Run mode clocking, or reset. A Run mode clocking change is initiated if the corresponding **RCGCACMP** bit is changed. A reset change is initiated if the corresponding **SRACMP** bit is changed from 0 to 1.

The **PRACMP** bit is cleared on any of the above events and is not set again until the module is completely powered, enabled, and internally reset.

Analog Comparator Peripheral Ready (PRACMP)

Base 0x400F.E000 Offset 0xA3C Type RO, reset 0x0000.0000

Reset



Bit/Field	Name	Type	Reset	Description
31:1	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
0	R0	RO	0	Analog Comparator Module 0 Peripheral Ready

- 1 The analog comparator module is ready for access.
- The analog comparator module is not ready for access. It is unclocked, unpowered, or in the process of completing a reset sequence.

Register 111: Pulse Width Modulator Peripheral Ready (PRPWM), offset 0xA40


The **PRPWM** register indicates whether the PWM modules are ready to be accessed by software following a change in status of power, Run mode clocking, or reset. A Run mode clocking change is initiated if the corresponding **RCGCPWM** bit is changed. A reset change is initiated if the corresponding **SRPWM** bit is changed from 0 to 1.

The **PRPWM** bit is cleared on any of the above events and is not set again until the module is completely powered, enabled, and internally reset.

Pulse Width Modulator Peripheral Ready (PRPWM)

Base 0x400F.E000 Offset 0xA40

Type RO, reset 0x0000.0000



Bit/Field	Name	Type	Reset	Description
31:2	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
1	R1	RO	0	PWM Module 1 Peripheral Ready
				Value Description
				1 PWM module 1 is ready for access.
				0 PWM module 1 is not ready for access. It is unclocked, unpowered, or in the process of completing a reset sequence.
0	R0	RO	0	PWM Module 0 Peripheral Ready

- 1 PWM module 0 is ready for access.
- 0 PWM module 0 is not ready for access. It is unclocked, unpowered, or in the process of completing a reset sequence.


Register 112: Quadrature Encoder Interface Peripheral Ready (PRQEI), offset 0xA44

The **PRQEI** register indicates whether the QEI modules are ready to be accessed by software following a change in status of power, Run mode clocking, or reset. A Run mode clocking change is initiated if the corresponding **RCGCQEI** bit is changed. A reset change is initiated if the corresponding **SRQEI** bit is changed from 0 to 1.

The **PRQEI** bit is cleared on any of the above events and is not set again until the module is completely powered, enabled, and internally reset.

Quadrature Encoder Interface Peripheral Ready (PRQEI)

Base 0x400F.E000 Offset 0xA44 Type RO, reset 0x0000.0000



Bit/Field	Name	Type	Reset	Description
31:2	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
1	R1	RO	0	QEI Module 1 Peripheral Ready
				Value Description
				1 QEI module 1 is ready for access.
				QEI module 1 is not ready for access. It is unclocked, unpowered, or in the process of completing a reset sequence.
0	R0	RO	0	QEI Module 0 Peripheral Ready

- 1 QEI module 0 is ready for access.
- QEI module 0 is not ready for access. It is unclocked, unpowered, or in the process of completing a reset sequence.

Register 113: EEPROM Peripheral Ready (PREEPROM), offset 0xA58


The **PREEPROM** register indicates whether the EEPROM module is ready to be accessed by software following a change in status of power, Run mode clocking, or reset. A Run mode clocking change is initiated if the corresponding **RCGCEEPROM** bit is changed. A reset change is initiated if the corresponding **SREEPROM** bit is changed from 0 to 1.

The **PREEPROM** bit is cleared on any of the above events and is not set again until the module is completely powered, enabled, and internally reset.

EEPROM Peripheral Ready (PREEPROM)

Base 0x400F.E000 Offset 0xA58

Type RO, reset 0x0000.0000



Bit/Field	Name	Type	Reset	Description
31:1	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
0	R0	RO	0	FEPROM Module Peripheral Ready

- 1 The EEPROM module is ready for access.
- The EEPROM module is not ready for access. It is unclocked, unpowered, or in the process of completing a reset sequence.

Register 114: 32/64-Bit Wide General-Purpose Timer Peripheral Ready (PRWTIMER), offset 0xA5C

The **PRWTIMER** register indicates whether the timer modules are ready to be accessed by software following a change in status of power, Run mode clocking, or reset. A Run mode clocking change is initiated if the corresponding **RCGCWTIMER** bit is changed. A reset change is initiated if the corresponding **SRWTIMER** bit is changed from 0 to 1.

The **PRWTIMER** bit is cleared on any of the above events and is not set again until the module is completely powered, enabled, and internally reset.

reserved

32/64-Bit Wide General-Purpose Timer Peripheral Ready (PRWTIMER)

Base 0x400F.E000 Offset 0xA5C Type RO, reset 0x0000.0000

3

R3

RO

30

Type Reset	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0
	15	14	13	12	11	10	9	8	7	6	5	4	3	2	1	0
	ſ		1 1		rese	rved	1 1				R5	R4	R3	R2	R1	R0
Type Reset	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0
E	Bit/Field		Nam	ne	Ту	Type Reset		Des	cription							
	31:6		reserv	R	0	0	com	ware sho patibility served ac	with futu	ıre produ	ucts, the	value of	a reserv			
	5		R5		R	0	0	32/64-Bit Wide General-Purpose Timer 5 Peripheral Ready								
								Valu	Value Description							
								1	32/64	-bit wide	e timer n	odule 5	is ready	for acce	ess.	
								0		cked, ur		nodule 5 d, or in th		•		
	4		R4		R	0	0	32/6	4-Bit Wid	de Gene	ral-Purp	ose Time	er 4 Peri	pheral R	eady	
								Valu	ue Desc	ription						
								1	32/64	-bit wide	e timer n	nodule 4	is ready	for acce	ess.	
								0	32/64	-bit wide	e timer n	nodule 4	is not re	ady for a	access. I	t is

Value Description

sequence.

1 32/64-bit wide timer module 3 is ready for access.

32/64-Bit Wide General-Purpose Timer 3 Peripheral Ready

32/64-bit wide timer module 3 is not ready for access. It is unclocked, unpowered, or in the process of completing a reset sequence.

unclocked, unpowered, or in the process of completing a reset

Bit/Field	Name	Туре	Reset	Description
2	R2	RO	0	32/64-Bit Wide General-Purpose Timer 2 Peripheral Ready
				 Value Description 32/64-bit wide timer module 2 is ready for access. 32/64-bit wide timer module 2 is not ready for access. It is unclocked, unpowered, or in the process of completing a reset sequence.
1	R1	RO	0	 32/64-Bit Wide General-Purpose Timer 1 Peripheral Ready Value Description 32/64-bit wide timer module 1 is ready for access. 32/64-bit wide timer module 1 is not ready for access. It is unclocked, unpowered, or in the process of completing a reset sequence.
0	R0	RO	0	 32/64-Bit Wide General-Purpose Timer 0 Peripheral Ready Value Description 32/64-bit wide timer module 0 is ready for access. 32/64-bit wide timer module 0 is not ready for access. It is unclocked, unpowered, or in the process of completing a reset sequence.

5.6 System Control Legacy Register Descriptions

All addresses given are relative to the System Control base address of 0x400F.E000.

Important: Register in this section are provided for legacy software support only; registers in "System Control Register Descriptions" on page 239 should be used instead.

Register 115: Device Capabilities 0 (DC0), offset 0x008

This legacy register is predefined by the part and can be used to verify features.


Important: This register is provided for legacy software support only.

The **Flash Size** (**FSIZE**) and **SRAM Size** (**SSIZE**) registers should be used to determine this microcontroller's memory sizes. A read of **DC0** correctly identifies legacy memory sizes but software must use **FSIZE** and **SSIZE** for memory sizes that are not listed below.

Device Capabilities 0 (DC0)

Base 0x400F.E000 Offset 0x008

Type RO, reset 0x007F.007F



Bit/Field Name Type Reset Description
31:16 SRAMSZ RO 0x7F SRAM Size

Indicates the size of the on-chip SRAM.

Value Description

0x7 2 KB of SRAM

0xF 4 KB of SRAM

0x17 6 KB of SRAM

0x1F 8 KB of SRAM

0x2F 12 KB of SRAM

0x3F 16 KB of SRAM

0x4F 20 KB of SRAM

0x5F 24 KB of SRAM

0x7F 32 KB of SRAM

Bit/Field	Name	Туре	Reset	Description
15:0	FLASHSZ	RO	0x7F	Flash Size Indicates the size of the on-chip Flash memory.
				Value Description
				0x3 8 KB of Flash
				0x7 16 KB of Flash
				0xF 32 KB of Flash
				0x1F 64 KB of Flash
				0x2F 96 KB of Flash
				0x3F 128 KB of Flash
				0x5F 192 KB of Flash
				0x7F 256 KB of Flash

Register 116: Device Capabilities 1 (DC1), offset 0x010

This register is predefined by the part and can be used to verify features. If any bit is clear in this register, the module is not present. The corresponding bit in the **RCGC0**, **SCGC0**, **DCGC0**, and the peripheral-specific **RCGC**, **SCGC**, and **DCGC** registers cannot be set.

Important: This register is provided for legacy software support only.

The Peripheral Present registers should be used to determine which modules are implemented on this microcontroller. A read of **DC1** correctly identifies if a legacy module is present but software must use the Peripheral Present registers to determine if a module is present that is not supported by the **DCn** registers.

Likewise, the ADC Peripheral Properties (ADCPP) register should be used to determine the maximum ADC sample rate and whether the temperature sensor is present. However, to support legacy software, the MAXADCnSPD fields and the TEMPSNS bit are available. A read of **DC1** correctly identifies the maximum ADC sample rate for legacy rates and whether the temperature sensor is present.

Device Capabilities 1 (DC1)

Base 0x400F.E000 Offset 0x010

Type RO, reset 0x1333.2FFF

	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16
		reserved		WDT1	rese	rved	CAN1	CAN0	rese	rved	PWM1	PWM0	rese	rved	ADC1	ADC0
Туре	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO
Reset	0	0	0	1	0	0	1	1	0	0	1	1	0	0	1	1
	15	14	13	12	11	10	9	8	7	6	5	4	3	2	1	0
		MINSY	'SDIV		MAXAD	C1SPD	MAXAD	COSPD	MPU	HIB	TEMPSNS	PLL	WDT0	swo	SWD	JTAG
Туре	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO
Reset	0	0	1	0	1	1	1	1	1	1	1	1	1	1	1	1

Bit/Field	Name	Туре	Reset	Description
31:29	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
28	WDT1	RO	0x1	Watchdog Timer1 Present
				When set, indicates that watchdog timer 1 is present.
27:26	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
25	CAN1	RO	0x1	CAN Module 1 Present
				When set, indicates that CAN unit 1 is present.
24	CAN0	RO	0x1	CAN Module 0 Present
				When set, indicates that CAN unit 0 is present.
23:22	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
21	PWM1	RO	0x1	PWM Module 1 Present
				When set, indicates that the PWM module is present.

Bit/Field	Name	Туре	Reset	Description
20	PWM0	RO	0x1	PWM Module 0 Present
				When set, indicates that the PWM module is present.
19:18	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
17	ADC1	RO	0x1	ADC Module 1 Present
				When set, indicates that ADC module 1 is present.
16	ADC0	RO	0x1	ADC Module 0 Present
				When set, indicates that ADC module 0 is present
15:12	MINSYSDIV	RO	0x2	System Clock Divider
				Minimum 4-bit divider value for system clock. The reset value is hardware-dependent. See the RCC register for how to change the system clock divisor using the SYSDIV bit.
				Value Description
				0x1 Specifies an 80-MHz CPU clock with a PLL divider of 2.5.
				0x2 Specifies a 66-MHz CPU clock with a PLL divider of 3.
				0x3 Specifies a 50-MHz CPU clock with a PLL divider of 4.
				0x4 Specifies a 40-MHz CPU clock with a PLL divider of 5.
				0x7 Specifies a 25-MHz clock with a PLL divider of 8.
				0x9 Specifies a 20-MHz clock with a PLL divider of 10.
11:10	MAXADC1SPD	RO	0x3	Max ADC1 Speed
				This field indicates the maximum rate at which the ADC samples data.
				Value Description
				0x3 1M samples/second
				0x2 500K samples/second
				0x1 250K samples/second
				0x0 125K samples/second
9:8	MAXADC0SPD	RO	0x3	Max ADC0 Speed
				This field indicates the maximum rate at which the ADC samples data.
				Value Description
				0x3 1M samples/second
				0x2 500K samples/second
				0x1 250K samples/second
				0x0 125K samples/second
7	MPU	RO	0x1	MPU Present
	-	-		When set, indicates that the Cortex-M4F Memory Protection Unit (MPU) module is present. See the "Cortex-M4F Peripherals" chapter for details on the MPU.

Bit/Field	Name	Туре	Reset	Description
6	HIB	RO	0x1	Hibernation Module Present When set, indicates that the Hibernation module is present.
5	TEMPSNS	RO	0x1	Temp Sensor Present When set, indicates that the on-chip temperature sensor is present.
4	PLL	RO	0x1	PLL Present When set, indicates that the on-chip Phase Locked Loop (PLL) is present.
3	WDT0	RO	0x1	Watchdog Timer 0 Present When set, indicates that watchdog timer 0 is present.
2	swo	RO	0x1	SWO Trace Port Present When set, indicates that the Serial Wire Output (SWO) trace port is present.
1	SWD	RO	0x1	SWD Present When set, indicates that the Serial Wire Debugger (SWD) is present.
0	JTAG	RO	0x1	JTAG Present When set, indicates that the JTAG debugger interface is present.

Register 117: Device Capabilities 2 (DC2), offset 0x014

This register is predefined by the part and can be used to verify features. If any bit is clear in this register, the module is not present. The corresponding bit in the **RCGC1**, **SCGC1**, **DCGC1**, and the peripheral-specific **RCGC**, **SCGC**, and **DCGC** registers registers cannot be set.

Important: This register is provided for legacy software support only.

The Peripheral Present registers should be used to determine which modules are implemented on this microcontroller. A read of **DC2** correctly identifies if a legacy module is present but software must use the Peripheral Present registers to determine if a module is present that is not supported by the **DCn** registers.

Note that the **Analog Comparator Peripheral Present (PPACMP)** register identifies whether the analog comparator module is present. The **Analog Comparator Peripheral Properties (ACMPPP)** register indicates how many analog comparator blocks are present in the module.

Device Capabilities 2 (DC2)

Base 0x400F.E000 Offset 0x014

Type RO, reset 0x070F.F337

	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16
	reserved	EPI0	reserved	1280	reserved	COMP2	COMP1	COMP0		rese	rved		TIMER3	TIMER2	TIMER1	TIMER0
Type	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO
Reset	0	0	0	0	0	1	1	1	0	0	0	0	1	1	1	1
	15	14	13	12	11	10	9	8	7	6	5	4	3	2	1	0
	I2C1HS	I2C1	I2C0HS	I2C0	rese	rved	QEI1	QEI0	rese	rved	SSI1	SSI0	reserved	UART2	UART1	UART0
Туре	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO
Reset	1	1	1	1	Λ	0	1	1	0	0	1	1	0	1	1	1

Bit/Field	Name	Туре	Reset	Description
31	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
30	EPI0	RO	0x0	EPI Module 0 Present
				When set, indicates that EPI module 0 is present.
29	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
28	1280	RO	0x0	I2S Module 0 Present
				When set, indicates that I2S module 0 is present.
27	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
26	COMP2	RO	0x1	Analog Comparator 2 Present
				When set, indicates that analog comparator 2 is present.
25	COMP1	RO	0x1	Analog Comparator 1 Present
				When set, indicates that analog comparator 1 is present.

Bit/Field	Name	Туре	Reset	Description
24	COMP0	RO	0x1	Analog Comparator 0 Present When set, indicates that analog comparator 0 is present.
23:20	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
19	TIMER3	RO	0x1	Timer Module 3 Present When set, indicates that General-Purpose Timer module 3 is present.
18	TIMER2	RO	0x1	Timer Module 2 Present When set, indicates that General-Purpose Timer module 2 is present.
17	TIMER1	RO	0x1	Timer Module 1 Present When set, indicates that General-Purpose Timer module 1 is present.
16	TIMER0	RO	0x1	Timer Module 0 Present When set, indicates that General-Purpose Timer module 0 is present.
15	I2C1HS	RO	0x1	I2C Module 1 Speed When set, indicates that I2C module 1 can operate in high-speed mode.
14	I2C1	RO	0x1	I2C Module 1 Present When set, indicates that I2C module 1 is present.
13	I2C0HS	RO	0x1	I2C Module 0 Speed When set, indicates that I2C module 0 can operate in high-speed mode.
12	I2C0	RO	0x1	I2C Module 0 Present When set, indicates that I2C module 0 is present.
11:10	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
9	QEI1	RO	0x1	QEI Module 1 Present When set, indicates that QEI module 1 is present.
8	QEI0	RO	0x1	QEI Module 0 Present When set, indicates that QEI module 0 is present.
7:6	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
5	SSI1	RO	0x1	SSI Module 1 Present When set, indicates that SSI module 1 is present.
4	SSI0	RO	0x1	SSI Module 0 Present When set, indicates that SSI module 0 is present.
3	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.

Bit/Field	Name	Type	Reset	Description
2	UART2	RO	0x1	UART Module 2 Present When set, indicates that UART module 2 is present.
1	UART1	RO	0x1	UART Module 1 Present When set, indicates that UART module 1 is present.
0	UART0	RO	0x1	UART Module 0 Present When set, indicates that UART module 0 is present.

Register 118: Device Capabilities 3 (DC3), offset 0x018

This register is predefined by the part and can be used to verify features. If any bit is clear in this register, the feature is not present.

Important: This register is provided for legacy software support only.

For some modules, the peripheral-resident Peripheral Properties registers should be used to determine which pins are available on this microcontroller. A read of **DC3** correctly identifies if a legacy pin is present but software must use the Peripheral Properties registers to determine if a pin is present that is not supported by the **DCn** registers.

Device Capabilities 3 (DC3)

Base 0x400F.E000 Offset 0x018

Type RO, reset 0xBFFF.FFFF

	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16
	32KHZ	reserved	CCP5	CCP4	CCP3	CCP2	CCP1	CCP0	ADC0AIN7	ADC0AIN6	ADC0AIN5	ADC0AIN4	ADC0AIN3	ADC0AIN2	ADC0AIN1	ADC0AIN0
Type	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO
Reset	1	0	1	1	1	1	1	1	1	1	1	1	1	1	1	1
	15	14	13	12	11	10	9	8	7	6	5	4	3	2	1	0
	PWMFAULT	C2O	C2PLUS	C2MINUS	C10	C1PLUS	C1MINUS	C0O	C0PLUS	C0MINUS	PWM5	PWM4	PWM3	PWM2	PWM1	PWM0
Type	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO
Reset	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1

Bit/Field	Name	Type	Reset	Description			
31	32KHZ	RO	0x1	32KHz Input Clock Available			
				When set, indicates an even CCP pin is present and can be used as a 32-KHz input clock.			
				Note: The GPTMPP register does not provide this information.			
30	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.			
29	CCP5	RO	0x1	T2CCP1 Pin Present			
				When set, indicates that Capture/Compare/PWM pin ${\tt T2CCP1}$ is present.			
				Note: The GPTMPP register does not provide this information.			
28	CCP4	RO	0x1	T2CCP0 Pin Present			
				When set, indicates that Capture/Compare/PWM pin ${\tt T2CCP0}$ is present.			
				Note: The GPTMPP register does not provide this information.			
27	CCP3	RO	0x1	T1CCP1 Pin Present			
				When set, indicates that Capture/Compare/PWM pin ${\tt TICCPI}$ is present.			
				Note: The GPTMPP register does not provide this information.			
26	CCP2	RO	0x1	T1CCP0 Pin Present			
				When set, indicates that Capture/Compare/PWM pin ${\tt T1CCP0}$ is present.			
				Note: The GPTMPP register does not provide this information.			

Bit/Field	Name	Туре	Reset	Description
25	CCP1	RO	0x1	T0CCP1 Pin Present When set, indicates that Capture/Compare/PWM pin T0CCP1 is present.
				Note: The GPTMPP register does not provide this information.
24	CCP0	RO	0x1	T0CCP0 Pin Present When set, indicates that Capture/Compare/PWM pin T0CCP0 is present.
				Note: The GPTMPP register does not provide this information.
23	ADC0AIN7	RO	0x1	ADC Module 0 AIN7 Pin Present When set, indicates that ADC module 0 input pin 7 is present.
				Note: The CH field in the ADCPP register provides this information.
22	ADC0AIN6	RO	0x1	ADC Module 0 AIN6 Pin Present When set, indicates that ADC module 0 input pin 6 is present.
				Note: The CH field in the ADCPP register provides this information.
21	ADC0AIN5	RO	0x1	ADC Module 0 AIN5 Pin Present When set, indicates that ADC module 0 input pin 5 is present.
				Note: The CH field in the ADCPP register provides this information.
20	ADC0AIN4	RO	0x1	ADC Module 0 AIN4 Pin Present When set, indicates that ADC module 0 input pin 4 is present.
				Note: The CH field in the ADCPP register provides this information.
19	ADC0AIN3	RO	0x1	ADC Module 0 AIN3 Pin Present When set, indicates that ADC module 0 input pin 3 is present.
				Note: The CH field in the ADCPP register provides this information.
18	ADC0AIN2	RO	0x1	ADC Module 0 AIN2 Pin Present When set, indicates that ADC module 0 input pin 2 is present.
				Note: The CH field in the ADCPP register provides this information.
17	ADC0AIN1	RO	0x1	ADC Module 0 AIN1 Pin Present When set, indicates that ADC module 0 input pin 1 is present.
				Note: The CH field in the ADCPP register provides this information.
16	ADC0AIN0	RO	0x1	ADC Module 0 AIN0 Pin Present When set, indicates that ADC module 0 input pin 0 is present.
				Note: The CH field in the ADCPP register provides this information.
15	PWMFAULT	RO	0x1	PWM Fault Pin Present When set, indicates that a PWM Fault pin is present. See DC5 for specific Fault pins on this device.
				Note: The FCNT field in the PWMPP register provides this information.
14	C2O	RO	0x1	C2o Pin Present When set, indicates that the analog comparator 2 output pin is present.
				Note: The C20 bit in the ACMPPP register provides this information.

Bit/Field	Name	Туре	Reset	Description		
13	C2PLUS	RO	0x1	C2+ Pin Present When set, indicates that the analog comparator 2 (+) input pin is present		
				Note: This pin is present when analog comparator 2 is present.		
12	C2MINUS	RO	0x1	C2- Pin Present When set, indicates that the analog comparator 2 (-) input pin is present.		
				Note: This pin is present when analog comparator 2 is present.		
11	C10	RO	0x1	C1o Pin Present When set, indicates that the analog comparator 1 output pin is present.		
				Note: The C10 bit in the ACMPPP register provides this information.		
10	C1PLUS	RO	0x1	C1+ Pin Present When set, indicates that the analog comparator 1 (+) input pin is present.		
				Note: This pin is present when analog comparator 1 is present.		
9	C1MINUS	RO	0x1	C1- Pin Present When set, indicates that the analog comparator 1 (-) input pin is present.		
				Note: This pin is present when analog comparator 1 is present.		
8	C0O	RO	0x1	C0o Pin Present When set, indicates that the analog comparator 0 output pin is present.		
7	COPLUS	RO	0x1	Note: The coo bit in the ACMPPP register provides this information. C0+ Pin Present When set, indicates that the analog comparator 0 (+) input pin is present. Note: This pin is present when analog comparator 0 is present.		
6	COMINUS	RO	0x1	C0- Pin Present When set, indicates that the analog comparator 0 (-) input pin is present. Note: This pin is present when analog comparator 0 is present.		
5	PWM5	RO	0x1	PWM5 Pin Present When set, indicates that the PWM pin 5 is present. Note: The GCNT field in the PWMPP register provides this		
4	PWM4	RO	0x1	information. PWM4 Pin Present When set, indicates that the PWM pin 4 is present. Note: The GCNT field in the PWMPP register provides this information.		
3	PWM3	RO	0x1	PWM3 Pin Present When set, indicates that the PWM pin 3 is present. Note: The GCNT field in the PWMPP register provides this information.		

Bit/Field	Name	Туре	Reset	Description
2	PWM2	RO	0x1	PWM2 Pin Present When set, indicates that the PWM pin 2 is present.
				Note: The GCNT field in the PWMPP register provides this information.
1	PWM1	RO	0x1	PWM1 Pin Present When set, indicates that the PWM pin 1 is present.
				Note: The GCNT field in the PWMPP register provides this information.
0	PWM0	RO	0x1	PWM0 Pin Present When set, indicates that the PWM pin 0 is present.
				Note: The GCNT field in the PWMPP register provides this information.

Register 119: Device Capabilities 4 (DC4), offset 0x01C

This register is predefined by the part and can be used to verify features. If any bit is clear in this register, the module is not present. The corresponding bit in the **RCGC2**, **SCGC2**, **DCGC2**, and the peripheral-specific **RCGC**, **SCGC**, and **DCGC** registers registers cannot be set.

Important: This register is provided for legacy software support only.

The Peripheral Present registers should be used to determine which modules are implemented on this microcontroller. A read of **DC4** correctly identifies if a legacy module is present but software must use the Peripheral Present registers to determine if a module is present that is not supported by the **DCn** registers.

The peripheral-resident Peripheral Properties registers should be used to determine which pins and features are available on this microcontroller. A read of **DC4** correctly identifies if a legacy pin or feature is present. Software must use the Peripheral Properties registers to determine if a pin or feature is present that is not supported by the **DCn** registers.

Device Capabilities 4 (DC4)

Base 0x400F.E000 Offset 0x01C

Type RO, reset 0x0004.F1FF

	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16
	reserved	EPHY0	reserved	EMAC0		reserved		E1588			reserved			PICAL	rese	rved
Type Reset	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 1	RO 0	RO 0
	15	14	13	12	11	10	9	8	7	6	5	4	3	2	1	0
	CCP7	CCP6	UDMA	ROM		reserved		GPIOJ	GPIOH	GPIOG	GPIOF	GPIOE	GPIOD	GPIOC	GPIOB	GPIOA
Type	RO 1	RO 1	RO 1	RO 1	RO 0	RO 0	RO 0	RO 1	RO 1	RO 1	RO 1	RO 1	RO 1	RO 1	RO 1	RO 1

Bit/Field	Name	Туре	Reset	Description
31	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
30	EPHY0	RO	0x0	Ethernet PHY Layer 0 Present When set, indicates that Ethernet PHY layer 0 is present.
29	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
28	EMAC0	RO	0x0	Ethernet MAC Layer 0 Present When set, indicates that Ethernet MAC layer 0 is present.
27:25	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
24	E1588	RO	0x0	1588 Capable When set, indicates that Ethernet MAC layer 0 is 1588 capable.

Bit/Field	Name	Туре	Reset	Description
23:19	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
18	PICAL	RO	0x1	PIOSC Calibrate
				When set, indicates that the PIOSC can be calibrated by software.
17:16	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
15	CCP7	RO	0x1	T3CCP1 Pin Present
				When set, indicates that Capture/Compare/PWM pin ${\tt T3CCP1}$ is present.
				Note: The GPTMPP register does not provide this information.
14	CCP6	RO	0x1	T3CCP0 Pin Present
				When set, indicates that Capture/Compare/PWM pin ${\tt T3CCP0}$ is present.
				Note: The GPTMPP register does not provide this information.
13	UDMA	RO	0x1	Micro-DMA Module Present
				When set, indicates that the micro-DMA module present.
12	ROM	RO	0x1	Internal Code ROM Present
				When set, indicates that internal code ROM is present.
11:9	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
8	GPIOJ	RO	0x1	GPIO Port J Present When set, indicates that GPIO Port J is present.
7	GPIOH	RO	0x1	GPIO Port H Present When set, indicates that GPIO Port H is present.
6	GPIOG	RO	0x1	GPIO Port G Present When set, indicates that GPIO Port G is present.
5	GPIOF	RO	0x1	GPIO Port F Present When set, indicates that GPIO Port F is present.
4	GPIOE	RO	0x1	GPIO Port E Present When set, indicates that GPIO Port E is present.
3	GPIOD	RO	0x1	GPIO Port D Present When set, indicates that GPIO Port D is present.
2	GPIOC	RO	0x1	GPIO Port C Present When set, indicates that GPIO Port C is present.
1	GPIOB	RO	0x1	GPIO Port B Present When set, indicates that GPIO Port B is present.

Bit/Field	Name	Туре	Reset	Description
0	GPIOA	RO	0x1	GPIO Port A Present
				When set, indicates that GPIO Port A is present.

Register 120: Device Capabilities 5 (DC5), offset 0x020

This register is predefined by the part and can be used to verify PWM features. If any bit is clear in this register, the module is not present.

Important: This register is provided for legacy software support only.

The **PWM Peripheral Properties (PWMPP)** register should be used to determine what pins and features are available on PWM modules. A read of this register correctly identifies if a legacy pin or feature is present. Software must use the **PWMPP** register to determine if a pin or feature that is not supported by the **DCn** registers is present.

Device Capabilities 5 (DC5)

Base 0x400F.E000 Offset 0x020

Type RO, reset 0x0F30.00FF

_	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16
Į	'	rese	erved		PWMFAULT3	PWMFAULT2		PWMFAULT0	rese	rved	PWMEFLT	PWMESYNC		rese	rved	
Type Reset	RO 0	RO 0	RO 0	RO 0	RO 1	RO 1	RO 1	RO 1	RO 0	RO 0	RO 1	RO 1	RO 0	RO 0	RO 0	RO 0
	15	14	13	12	11	10	9	8	7	6	5	4	3	2	1	0
ſ	,			rese	erved				PWM7	PWM6	PWM5	PWM4	PWM3	PWM2	PWM1	PWM0
Type Reset	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 1	RO 1	RO 1	RO 1	RO 1	RO 1	RO 1	RO 1
В	it/Field		Nam	ne	Ту	ре	Reset	Des	cription							
;	31:28		reserv	ved	R	0	0	com	patibility	with futu	ıre produ	ne value ucts, the lify-write	value of	a reserv		
	27		PWMFA	ULT3	R	0	0x1			3 Pin Pre dicates t		PWM Fai	ult 3 pin	is presei	nt.	
	26		PWMFA	ULT2	R	0	0x1			2 Pin Pre dicates t		PWM Fai	ult 2 pin	is presei	nt.	
	25		PWMFA	ULT1	R	0	0x1			l Pin Pre dicates t		PWM Fai	ult 1 pin	is presei	nt.	
	24		PWMFA	ULT0	R	0	0x1) Pin Pre dicates t		PWM Fai	ult 0 pin	is prese	nt.	
:	23:22		reserv	ved	R	0	0	com	patibility	with futu	ıre produ	ne value ucts, the lify-write	value of	a reserv		
	21		PWME	FLT	R	0	0x1			ded Faul dicates t		PWM Ext	tended F	ault feat	ure is ac	ctive.
	20		PWMES	SYNC	R	0	0x1			ded SYN dicates t		e PWM Ext	tended S	SYNC fea	ature is a	active.
	19:8		reserv	ved	R	0	0	com	patibility	with futu	ure produ	ne value ucts, the lify-write	value of	a reserv		

Bit/Field	Name	Туре	Reset	Description
7	PWM7	RO	0x1	PWM7 Pin Present When set, indicates that the PWM pin 7 is present.
6	PWM6	RO	0x1	PWM6 Pin Present When set, indicates that the PWM pin 6 is present.
5	PWM5	RO	0x1	PWM5 Pin Present When set, indicates that the PWM pin 5 is present.
4	PWM4	RO	0x1	PWM4 Pin Present When set, indicates that the PWM pin 4 is present.
3	PWM3	RO	0x1	PWM3 Pin Present When set, indicates that the PWM pin 3 is present.
2	PWM2	RO	0x1	PWM2 Pin Present When set, indicates that the PWM pin 2 is present.
1	PWM1	RO	0x1	PWM1 Pin Present When set, indicates that the PWM pin 1 is present.
0	PWM0	RO	0x1	PWM0 Pin Present When set, indicates that the PWM pin 0 is present.

Register 121: Device Capabilities 6 (DC6), offset 0x024

This register is predefined by the part and can be used to verify features. If any bit is clear in this register, the module is not present. The corresponding bit in the **RCGC0**, **SCGC0**, and **DCGC0** registers cannot be set.


Important: This register is provided for legacy software support only.

The **USB Peripheral Properties (USBPP)** register should be used to determine what features are available on the USB module. A read of this register correctly identifies if a legacy feature is present. Software must use the **USBPP** register to determine if a pin or feature that is not supported by the **DCn** registers is present.

Device Capabilities 6 (DC6)

Base 0x400F.E000 Offset 0x024

Type RO, reset 0x0000.0013



Bit/Field	Name	Type	Reset	Description
31:5	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
4	USB0PHY	RO	0x1	USB Module 0 PHY Present When set, indicates that the USB module 0 PHY is present.
3:2	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
1:0	USB0	RO	0x3	USB Module 0 Present This field indicates that USB module 0 is present and specifies its

sysValue Description

0x0 NA

capability.

USB0 is not present.

0x1 DEVICE

USB0 is Device Only.

0x2 HOST

USB0 is Device or Host.

0x3 OTG

USB0 is OTG.

Register 122: Device Capabilities 7 (DC7), offset 0x028


This register is predefined by the part and can be used to verify μ DMA channel features. A 1 indicates the channel is available on this device; a 0 that the channel is only available on other devices in the family. Channels can have multiple assignments, see "Channel Assignments" on page 584 for more information.

Important: This register is provided for legacy software support only. The DMACHANS bit field in the **DMA Status (DMASTAT)** register indicates the number of DMA channels.

Device Capabilities 7 (DC7)

Base 0x400F.E000 Offset 0x028

Type RO, reset 0xFFFF.FFF



Bit/Field	Name	Type	Reset	Description
31	reserved	RO	0x1	DMA Channel 31 When set, indicates µDMA channel 31 is available.
30	DMACH30	RO	0x1	DMA Channel 30 When set, indicates µDMA channel 30 is available.
29	DMACH29	RO	0x1	DMA Channel 29 When set, indicates µDMA channel 29 is available.
28	DMACH28	RO	0x1	DMA Channel 28 When set, indicates µDMA channel 28 is available.
27	DMACH27	RO	0x1	DMA Channel 27 When set, indicates µDMA channel 27 is available.
26	DMACH26	RO	0x1	DMA Channel 26 When set, indicates μDMA channel 26 is available.
25	DMACH25	RO	0x1	DMA Channel 25 When set, indicates μDMA channel 25 is available.
24	DMACH24	RO	0x1	DMA Channel 24 When set, indicates μDMA channel 24 is available.
23	DMACH23	RO	0x1	DMA Channel 23 When set, indicates μDMA channel 23 is available.
22	DMACH22	RO	0x1	DMA Channel 22 When set, indicates µDMA channel 22 is available.

Bit/Field	Name	Туре	Reset	Description
21	DMACH21	RO	0x1	DMA Channel 21 When set, indicates μDMA channel 21 is available.
20	DMACH20	RO	0x1	DMA Channel 20 When set, indicates μDMA channel 20 is available.
19	DMACH19	RO	0x1	DMA Channel 19 When set, indicates µDMA channel 19 is available.
18	DMACH18	RO	0x1	DMA Channel 18 When set, indicates µDMA channel 18 is available.
17	DMACH17	RO	0x1	DMA Channel 17 When set, indicates µDMA channel 17 is available.
16	DMACH16	RO	0x1	DMA Channel 16 When set, indicates µDMA channel 16 is available.
15	DMACH15	RO	0x1	DMA Channel 15 When set, indicates µDMA channel 15 is available.
14	DMACH14	RO	0x1	DMA Channel 14 When set, indicates µDMA channel 14 is available.
13	DMACH13	RO	0x1	DMA Channel 13 When set, indicates µDMA channel 13 is available.
12	DMACH12	RO	0x1	DMA Channel 12 When set, indicates µDMA channel 12 is available.
11	DMACH11	RO	0x1	DMA Channel 11 When set, indicates μDMA channel 11 is available.
10	DMACH10	RO	0x1	DMA Channel 10 When set, indicates µDMA channel 10 is available.
9	DMACH9	RO	0x1	DMA Channel 9 When set, indicates µDMA channel 9 is available.
8	DMACH8	RO	0x1	DMA Channel 8 When set, indicates µDMA channel 8 is available.
7	DMACH7	RO	0x1	DMA Channel 7 When set, indicates µDMA channel 7 is available.
6	DMACH6	RO	0x1	DMA Channel 6 When set, indicates µDMA channel 6 is available.
5	DMACH5	RO	0x1	DMA Channel 5 When set, indicates µDMA channel 5 is available.
4	DMACH4	RO	0x1	DMA Channel 4 When set, indicates µDMA channel 4 is available.

Bit/Field	Name	Type	Reset	Description
3	DMACH3	RO	0x1	DMA Channel 3 When set, indicates µDMA channel 3 is available.
2	DMACH2	RO	0x1	DMA Channel 2 When set, indicates µDMA channel 2 is available.
1	DMACH1	RO	0x1	DMA Channel 1 When set, indicates µDMA channel 1 is available.
0	DMACH0	RO	0x1	DMA Channel 0 When set, indicates µDMA channel 0 is available.

Register 123: Device Capabilities 8 (DC8), offset 0x02C

This register is predefined by the part and can be used to verify features.

Important: This register is provided for legacy software support only.

The **ADC Peripheral Properties (ADCPP)** register should be used to determine how many input channels are available on the ADC module. A read of this register correctly identifies if legacy channels are present but software must use the **ADCPP** register to determine if a channel is present that is not supported by the **DCn** registers.

Device Capabilities 8 (DC8)

Base 0x400F.E000

Offset 0x02C Type RO, reset 0xFFFF.FFFF

	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16
	ADC1AIN15	ADC1AIN14	ADC1AIN13	ADC1AIN12	ADC1AIN11	ADC1AIN10	ADC1AIN9	ADC1AIN8	ADC1AIN7	ADC1AIN6	ADC1AIN5	ADC1AIN4	ADC1AIN3	ADC1AIN2	ADC1AIN1	ADC1AIN0
Type	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO
Reset	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1
	15	14	13	12	11	10	9	8	7	6	5	4	3	2	1	0
	ADC0AIN15	ADC0AIN14	ADC0AIN13	ADC0AIN12	ADC0AIN11	ADC0AIN10	ADC0AIN9	ADC0AIN8	ADC0AIN7	ADC0AIN6	ADC0AIN5	ADC0AIN4	ADC0AIN3	ADC0AIN2	ADC0AIN1	ADC0AIN0
Type	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO
Reset	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1

Bit/Field	Name	Туре	Reset	Description
31	ADC1AIN15	RO	0x1	ADC Module 1 AIN15 Pin Present When set, indicates that ADC module 1 input pin 15 is present.
30	ADC1AIN14	RO	0x1	ADC Module 1 AIN14 Pin Present When set, indicates that ADC module 1 input pin 14 is present.
29	ADC1AIN13	RO	0x1	ADC Module 1 AIN13 Pin Present When set, indicates that ADC module 1 input pin 13 is present.
28	ADC1AIN12	RO	0x1	ADC Module 1 AIN12 Pin Present When set, indicates that ADC module 1 input pin 12 is present.
27	ADC1AIN11	RO	0x1	ADC Module 1 AIN11 Pin Present When set, indicates that ADC module 1 input pin 11 is present.
26	ADC1AIN10	RO	0x1	ADC Module 1 AIN10 Pin Present When set, indicates that ADC module 1 input pin 10 is present.
25	ADC1AIN9	RO	0x1	ADC Module 1 AIN9 Pin Present When set, indicates that ADC module 1 input pin 9 is present.
24	ADC1AIN8	RO	0x1	ADC Module 1 AIN8 Pin Present When set, indicates that ADC module 1 input pin 8 is present.
23	ADC1AIN7	RO	0x1	ADC Module 1 AIN7 Pin Present When set, indicates that ADC module 1 input pin 7 is present.
22	ADC1AIN6	RO	0x1	ADC Module 1 AIN6 Pin Present When set, indicates that ADC module 1 input pin 6 is present.

Bit/Field	Name	Туре	Reset	Description
21	ADC1AIN5	RO	0x1	ADC Module 1 AIN5 Pin Present When set, indicates that ADC module 1 input pin 5 is present.
20	ADC1AIN4	RO	0x1	ADC Module 1 AIN4 Pin Present When set, indicates that ADC module 1 input pin 4 is present.
19	ADC1AIN3	RO	0x1	ADC Module 1 AIN3 Pin Present When set, indicates that ADC module 1 input pin 3 is present.
18	ADC1AIN2	RO	0x1	ADC Module 1 AIN2 Pin Present When set, indicates that ADC module 1 input pin 2 is present.
17	ADC1AIN1	RO	0x1	ADC Module 1 AIN1 Pin Present When set, indicates that ADC module 1 input pin 1 is present.
16	ADC1AIN0	RO	0x1	ADC Module 1 AIN0 Pin Present When set, indicates that ADC module 1 input pin 0 is present.
15	ADC0AIN15	RO	0x1	ADC Module 0 AIN15 Pin Present When set, indicates that ADC module 0 input pin 15 is present.
14	ADC0AIN14	RO	0x1	ADC Module 0 AIN14 Pin Present When set, indicates that ADC module 0 input pin 14 is present.
13	ADC0AIN13	RO	0x1	ADC Module 0 AIN13 Pin Present When set, indicates that ADC module 0 input pin 13 is present.
12	ADC0AIN12	RO	0x1	ADC Module 0 AIN12 Pin Present When set, indicates that ADC module 0 input pin 12 is present.
11	ADC0AIN11	RO	0x1	ADC Module 0 AIN11 Pin Present When set, indicates that ADC module 0 input pin 11 is present.
10	ADC0AIN10	RO	0x1	ADC Module 0 AIN10 Pin Present When set, indicates that ADC module 0 input pin 10 is present.
9	ADC0AIN9	RO	0x1	ADC Module 0 AIN9 Pin Present When set, indicates that ADC module 0 input pin 9 is present.
8	ADC0AIN8	RO	0x1	ADC Module 0 AIN8 Pin Present When set, indicates that ADC module 0 input pin 8 is present.
7	ADC0AIN7	RO	0x1	ADC Module 0 AIN7 Pin Present When set, indicates that ADC module 0 input pin 7 is present.
6	ADC0AIN6	RO	0x1	ADC Module 0 AIN6 Pin Present When set, indicates that ADC module 0 input pin 6 is present.
5	ADC0AIN5	RO	0x1	ADC Module 0 AIN5 Pin Present When set, indicates that ADC module 0 input pin 5 is present.
4	ADC0AIN4	RO	0x1	ADC Module 0 AIN4 Pin Present When set, indicates that ADC module 0 input pin 4 is present.

Bit/Field	Name	Туре	Reset	Description
3	ADC0AIN3	RO	0x1	ADC Module 0 AIN3 Pin Present When set, indicates that ADC module 0 input pin 3 is present.
2	ADC0AIN2	RO	0x1	ADC Module 0 AIN2 Pin Present When set, indicates that ADC module 0 input pin 2 is present.
1	ADC0AIN1	RO	0x1	ADC Module 0 AIN1 Pin Present When set, indicates that ADC module 0 input pin 1 is present.
0	ADC0AIN0	RO	0x1	ADC Module 0 AIN0 Pin Present When set, indicates that ADC module 0 input pin 0 is present.

Register 124: Software Reset Control 0 (SRCR0), offset 0x040

This register allows individual modules to be reset. Writes to this register are masked by the bits in the **Device Capabilities 1 (DC1)** register.

Important: This register is provided for legacy software support only.

The peripheral-specific Software Reset registers (such as **SRWD**) should be used to reset specific peripherals. A write to this legacy register also writes the corresponding bit in the peripheral-specific register. Any bits that are changed by writing to this legacy register can be read back correctly with a read of this register. Software must use the peripheral-specific registers to support modules that are not present in the legacy registers. If software uses a peripheral-specific register to write a legacy peripheral (such as Watchdog 1), the write causes proper operation, but the value of that bit is not reflected in this register. If software uses both legacy and peripheral-specific register accesses, the peripheral-specific registers must be accessed by read-modify-write operations that affect only peripherals that are not present in the legacy registers. In this manner, both the peripheral-specific and legacy registers have coherent information.

Software Reset Control 0 (SRCR0)

Base 0x400F.E000 Offset 0x040 Type RO, reset 0x0000.0000

_	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16
		reserved		WDT1	rese	rved	CAN1	CAN0		reserved		PWM0	rese	rved	ADC1	ADC0
Type	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO
Reset	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0
	15	14	13	12	11	10	9	8	7	6	5	4	3	2	1	0
		' '		1	reserved		1	1		НІВ	rese	erved	WDT0		reserved	
Type '	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO
Reset	Λ	0	Λ	Ω	0	0	0	0	0	Ω	0	0	0	0	Ω	0

Bit/Field	Name	Туре	Reset	Description
31:29	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
28	WDT1	RO	0x0	WDT1 Reset Control When this bit is set, Watchdog Timer module 1 is reset. All internal data is lost and the registers are returned to their reset states. This bit must be manually cleared after being set.
27:26	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
25	CAN1	RO	0x0	CAN1 Reset Control When this bit is set, CAN module 1 is reset. All internal data is lost and the registers are returned to their reset states. This bit must be manually cleared after being set.
24	CAN0	RO	0x0	CAN0 Reset Control When this bit is set, CAN module 0 is reset. All internal data is lost and the registers are returned to their reset states. This bit must be manually cleared after being set.

Bit/Field	Name	Туре	Reset	Description
23:21	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
20	PWM0	RO	0x0	PWM Reset Control
				When this bit is set, PWM module 0 is reset. All internal data is lost and the registers are returned to their reset states. This bit must be manually cleared after being set.
19:18	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
17	ADC1	RO	0x0	ADC1 Reset Control
				When this bit is set, ADC module 1 is reset. All internal data is lost and the registers are returned to their reset states. This bit must be manually cleared after being set.
16	ADC0	RO	0x0	ADC0 Reset Control
				When this bit is set, ADC module 0 is reset. All internal data is lost and the registers are returned to their reset states. This bit must be manually cleared after being set.
15:7	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
6	HIB	RO	0x0	HIB Reset Control
				When this bit is set, the Hibernation module is reset. All internal data is lost and the registers are returned to their reset states. This bit must be manually cleared after being set.
5:4	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
3	WDT0	RO	0x0	WDT0 Reset Control
				When this bit is set, Watchdog Timer module 0 is reset. All internal data is lost and the registers are returned to their reset states. This bit must be manually cleared after being set.
2:0	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.

Register 125: Software Reset Control 1 (SRCR1), offset 0x044

This register allows individual modules to be reset. Writes to this register are masked by the bits in the **Device Capabilities 2 (DC2)** register.

Important: This register is provided for legacy software support only.

The peripheral-specific Software Reset registers (such as **SRTIMER**) should be used to reset specific peripherals. A write to this register also writes the corresponding bit in the peripheral-specific register. Any bits that are changed by writing to this register can be read back correctly with a read of this register. Software must use the peripheral-specific registers to support modules that are not present in the legacy registers. If software uses a peripheral-specific register to write a legacy peripheral (such as TIMER0), the write causes proper operation, but the value of that bit is not reflected in this register. If software uses both legacy and peripheral-specific register accesses, the peripheral-specific registers must be accessed by read-modify-write operations that affect only peripherals that are not present in the legacy registers. In this manner, both the peripheral-specific and legacy registers have coherent information.

Note that the **Software Reset Analog Comparator (SRACMP)** register has only one bit to set the analog comparator module. Resetting the module resets all the blocks. If any of the COMPn bits are set, the entire analog comparator module is reset. It is not possible to reset the blocks individually.

Software Reset Control 1 (SRCR1)

Base 0x400F.E000 Offset 0x044 Type RO, reset 0x0000.0000

	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16
			reserved			COMP2	COMP1	COMP0		rese	rved	1	TIMER3	TIMER2	TIMER1	TIMER0
Туре	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO
Reset	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0
	15	14	13	12	11	10	9	8	7	6	5	4	3	2	1	0
	reserved	I2C1	reserved	I2C0	rese	rved	QEI1	QEI0	rese	rved	SSI1	SSI0	reserved	UART2	UART1	UART0
Type	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO
Donot	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0

Bit/Field	Name	Type	Reset	Description
31:27	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
26	COMP2	RO	0x0	Analog Comp 2 Reset Control
				When this bit is set, Analog Comparator module 2 is reset. All internal data is lost and the registers are returned to their reset states. This bit must be manually cleared after being set.
25	COMP1	RO	0x0	Analog Comp 1 Reset Control
				When this bit is set, Analog Comparator module 1 is reset. All internal data is lost and the registers are returned to their reset states. This bit must be manually cleared after being set.

Bit/Field	Name	Туре	Reset	Description
24	COMP0	RO	0x0	Analog Comp 0 Reset Control When this bit is set, Analog Comparator module 0 is reset. All internal data is lost and the registers are returned to their reset states. This bit must be manually cleared after being set.
23:20	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
19	TIMER3	RO	0x0	Timer 3 Reset Control Timer 3 Reset Control. When this bit is set, General-Purpose Timer module 3 is reset. All internal data is lost and the registers are returned to their reset states. This bit must be manually cleared after being set.
18	TIMER2	RO	0x0	Timer 2 Reset Control When this bit is set, General-Purpose Timer module 2 is reset. All internal data is lost and the registers are returned to their reset states. This bit must be manually cleared after being set.
17	TIMER1	RO	0x0	Timer 1 Reset Control When this bit is set, General-Purpose Timer module 1 is reset. All internal data is lost and the registers are returned to their reset states. This bit must be manually cleared after being set.
16	TIMER0	RO	0x0	Timer 0 Reset Control When this bit is set, General-Purpose Timer module 0 is reset. All internal data is lost and the registers are returned to their reset states. This bit must be manually cleared after being set.
15	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
14	I2C1	RO	0x0	I2C1 Reset Control When this bit is set, I2C module 1 is reset. All internal data is lost and the registers are returned to their reset states. This bit must be manually cleared after being set.
13	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
12	I2C0	RO	0x0	I2C0 Reset Control When this bit is set, I2C module 0 is reset. All internal data is lost and the registers are returned to their reset states. This bit must be manually cleared after being set.
11:10	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
9	QEI1	RO	0x0	QEI1 Reset Control When this bit is set, QEI module 1 is reset. All internal data is lost and the registers are returned to their reset states. This bit must be manually cleared after being set.

Bit/Field	Name	Туре	Reset	Description
8	QEI0	RO	0x0	QEI0 Reset Control When this bit is set, QEI module 0 is reset. All internal data is lost and the registers are returned to their reset states. This bit must be manually cleared after being set.
7:6	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
5	SSI1	RO	0x0	SSI1 Reset Control When this bit is set, SSI module 1 is reset. All internal data is lost and the registers are returned to their reset states. This bit must be manually cleared after being set.
4	SSI0	RO	0x0	SSI0 Reset Control When this bit is set, SSI module 0 is reset. All internal data is lost and the registers are returned to their reset states. This bit must be manually cleared after being set.
3	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
2	UART2	RO	0x0	UART2 Reset Control When this bit is set, UART module 2 is reset. All internal data is lost and the registers are returned to their reset states. This bit must be manually cleared after being set.
1	UART1	RO	0x0	UART1 Reset Control When this bit is set, UART module 1 is reset. All internal data is lost and the registers are returned to their reset states. This bit must be manually cleared after being set.
0	UART0	RO	0x0	UART0 Reset Control When this bit is set, UART module 0 is reset. All internal data is lost and the registers are returned to their reset states. This bit must be manually cleared after being set.

Register 126: Software Reset Control 2 (SRCR2), offset 0x048

This register allows individual modules to be reset. Writes to this register are masked by the bits in the **Device Capabilities 4 (DC4)** register.

Important: This register is provided for legacy software support only.

The peripheral-specific Software Reset registers (such as **SRDMA**) should be used to reset specific peripherals. A write to this legacy register also writes the corresponding bit in the peripheral-specific register. Any bits that are changed by writing to this register can be read back correctly with a read of this register. Software must use the peripheral-specific registers to support modules that are not present in the legacy registers. If software uses a peripheral-specific register to write a legacy peripheral (such as the μ DMA), the write causes proper operation, but the value of that bit is not reflected in this register. If software uses both legacy and peripheral-specific register accesses, the peripheral-specific registers must be accessed by read-modify-write operations that affect only peripherals that are not present in the legacy registers. In this manner, both the peripheral-specific and legacy registers have coherent information.

Software Reset Control 2 (SRCR2)

Base 0x400F.E000 Offset 0x048 Type RO, reset 0x0000.0000

_	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16
			'	1	i I			reserved	I I							USB0
Type	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO
Reset	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0
	15	14	13	12	11	10	9	8	7	6	5	4	3	2	1	0
	rese	rved	UDMA		rese	rved		GPIOJ	GPIOH	GPIOG	GPIOF	GPIOE	GPIOD	GPIOC	GPIOB	GPIOA
Type	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO
Reset	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0

Bit/Field	Name	Туре	Reset	Description
31:17	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
16	USB0	RO	0x0	USB0 Reset Control
				When this bit is set, USB module 0 is reset. All internal data is lost and the registers are returned to their reset states. This bit must be manually cleared after being set.
15:14	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
13	UDMA	RO	0x0	Micro-DMA Reset Control
				When this bit is set, uDMA module is reset. All internal data is lost and the registers are returned to their reset states. This bit must be manually cleared after being set.
12:9	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.

Bit/Field	Name	Туре	Reset	Description
8	GPIOJ	RO	0x0	Port J Reset Control When this bit is set, Port J module is reset. All internal data is lost and the registers are returned to their reset states. This bit must be manually cleared after being set.
7	GPIOH	RO	0x0	Port H Reset Control When this bit is set, Port H module is reset. All internal data is lost and the registers are returned to their reset states. This bit must be manually cleared after being set.
6	GPIOG	RO	0x0	Port G Reset Control When this bit is set, Port G module is reset. All internal data is lost and the registers are returned to their reset states. This bit must be manually cleared after being set.
5	GPIOF	RO	0x0	Port F Reset Control When this bit is set, Port F module is reset. All internal data is lost and the registers are returned to their reset states. This bit must be manually cleared after being set.
4	GPIOE	RO	0x0	Port E Reset Control When this bit is set, Port E module is reset. All internal data is lost and the registers are returned to their reset states. This bit must be manually cleared after being set.
3	GPIOD	RO	0x0	Port D Reset Control When this bit is set, Port D module is reset. All internal data is lost and the registers are returned to their reset states. This bit must be manually cleared after being set.
2	GPIOC	RO	0x0	Port C Reset Control When this bit is set, Port C module is reset. All internal data is lost and the registers are returned to their reset states. This bit must be manually cleared after being set.
1	GPIOB	RO	0x0	Port B Reset Control When this bit is set, Port B module is reset. All internal data is lost and the registers are returned to their reset states. This bit must be manually cleared after being set.
0	GPIOA	RO	0x0	Port A Reset Control When this bit is set, Port A module is reset. All internal data is lost and the registers are returned to their reset states. This bit must be manually cleared after being set.

Register 127: Run Mode Clock Gating Control Register 0 (RCGC0), offset 0x100

This register controls the clock gating logic in normal Run mode. Each bit controls a clock enable for a given interface, function, or module. If set, the module receives a clock and functions. Otherwise, the module is unclocked and disabled (saving power). If the module is unclocked, reads or writes to the module generate a bus fault. The reset state of these bits is 0 (unclocked) unless otherwise noted, so that all functional modules are disabled. It is the responsibility of software to enable the ports necessary for the application. Note that these registers may contain more bits than there are interfaces, functions, or modules to control. This configuration is implemented to assure reasonable code compatibility with other family and future parts. **RCGC0** is the clock configuration register for running operation, **SCGC0** for Sleep operation, and **DCGC0** for Deep-Sleep operation. Setting the ACG bit in the **Run-Mode Clock Configuration (RCC)** register specifies that the system uses sleep modes. Note that there must be a delay of 3 system clocks after a module clock is enabled before any registers in that module are accessed.

Important: This register is provided for legacy software support only.

The peripheral-specific Run Mode Clock Gating Control registers (such as **RCGCWD**) should be used to reset specific peripherals. A write to this legacy register also writes the corresponding bit in the peripheral-specific register. Any bits that are changed by writing to this register can be read back correctly with a read of this register. Software must use the peripheral-specific registers to support modules that are not present in the legacy registers. If software uses a peripheral-specific register to write a legacy peripheral (such as Watchdog 1), the write causes proper operation, but the value of that bit is not reflected in this register. If software uses both legacy and peripheral-specific register accesses, the peripheral-specific registers must be accessed by read-modify-write operations that affect only peripherals that are not present in the legacy registers. In this manner, both the peripheral-specific and legacy registers have coherent information.

Likewise, the ADC Peripheral Configuration (ADCPC) register should be used to configure the ADC sample rate. However, to support legacy software, the MAXADCnSPD fields are available. A write to these legacy fields also writes the corresponding field in the peripheral-specific register. If a field is changed by writing to this register, it can be read back correctly with a read of this register. Software must use the peripheral-specific registers to support rates that are not available in this register. If software uses a peripheral-specific register to set the ADC rate, the write causes proper operation, but the value of that field is not reflected in this register. If software uses both legacy and peripheral-specific register accesses, the peripheral-specific registers must be accessed by read-modify-write operations that affect only peripherals that are not present in the legacy registers. In this manner, both the peripheral-specific and legacy registers have coherent information.

Run Mode Clock Gating Control Register 0 (RCGC0)

Base 0x400F.E000 Offset 0x100 Type RO, reset 0x0000.0040

rype	RO, rese	t uxuuuu.c	1040													
	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16
	\ \ \ \ \ \ \ \ \ \ \ \ \ \ \ \ \ \ \	reserved		WDT1	rese	rved	CAN1	CAN0		reserved	l	PWM0	rese	rved	ADC1	ADC0
Type Reset	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0
	15	14	13	12	11	10	9	8	7	6	5	4	3	2	1	0
		reser	ved	1	MAXAD	C1SPD	MAXAE	I DC0SPD	reserved	HIB	rese	l erved	WDT0		reserved	
Type Reset	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 1	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0
E	Bit/Field		Nan	ne	Ту	ре	Reset	Des	cription							
	31:29		reser	ved	R	0	0								t. To prov	
												dify-write			vou bit oi	iouiu bo
	28		WD ⁻	Γ1	R	0	0x0	WD	T1 Clock	Gating	Control					
															ner modu wise, the	
								is u		and disa	abled. If	the mod			, a read o	
	07.00				_	_	•									
	27:26		reser	vea	R	O	0	con	npatibility	with futu	ire prod	ucts, the	value of	a reser	t. To prov ved bit sh	
								pres	served a	cross a r	ead-mo	dify-write	operation	n.		
	25		CAN	N1	R	0	0x0		N1 Clock	_						
								rece	eives a cl	ock and	function	s. Otherv	vise, the	module	set, the is uncloconto the mod	ked and
									erates a			olocica,	a read of	will to	o uno mod	auic
	24		CAN	10	R	0	0x0	CAI	N0 Clock	Gating (Control					
															set, the	
								disa		he modu	le is un				the mod	
	23:21		reser	ved	R	0	0					he value	of a res	erved hi	t. To prov	vide
	20.21		1000.	vou		C	Ü	con	npatibility	with futu	ıre prod		value of	a reser	ved bit sh	
	20		PWN	M0	R	0	0x0	PW	M Clock	Gating C	Control					
								rece disa	eives a cl	ock and t he modu	function le is un	s. Otherv	vise, the	module	If set, the is uncloc the mod	ked and
	19:18		reser	ved	R	0	0	con	npatibility	with futu	ıre prod		value of	a reser	t. To prov	

preserved across a read-modify-write operation.

Bit/Field	Name	Туре	Reset	Description
17	ADC1	RO	0x0	ADC1 Clock Gating Control This bit controls the clock gating for SAR ADC module 1. If set, the module receives a clock and functions. Otherwise, the module is unclocked and disabled. If the module is unclocked, a read or write to the module generates a bus fault.
16	ADC0	RO	0x0	ADC0 Clock Gating Control This bit controls the clock gating for ADC module 0. If set, the module receives a clock and functions. Otherwise, the module is unclocked and disabled. If the module is unclocked, a read or write to the module generates a bus fault.
15:12	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
11:10	MAXADC1SPD	RO	0x0	ADC1 Sample Speed This field sets the rate at which ADC module 1 samples data. You cannot set the rate higher than the maximum rate. You can set the sample rate by setting the MAXADC1SPD bit as follows (all other encodings are reserved):
				Value Description 0x3 1M samples/second 0x2 500K samples/second 0x1 250K samples/second 0x0 125K samples/second
9:8	MAXADC0SPD	RO	0x0	ADC0 Sample Speed This field sets the rate at which ADC0 samples data. You cannot set the rate higher than the maximum rate. You can set the sample rate by setting the MAXADC0SPD bit as follows (all other encodings are reserved): Value Description 0x3 1M samples/second 0x2 500K samples/second
7	reserved	RO	0	Ox0 125K samples/second Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
6	HIB	RO	0x1	HIB Clock Gating Control This bit controls the clock gating for the Hibernation module. If set, the module receives a clock and functions. Otherwise, the module is unclocked and disabled. If the module is unclocked, a read or write to the module generates a bus fault.
5:4	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.

Bit/Field	Name	Туре	Reset	Description
3	WDT0	RO	0x0	WDT0 Clock Gating Control This bit controls the clock gating for the Watchdog Timer module 0. If set, the module receives a clock and functions. Otherwise, the module is unclocked and disabled. If the module is unclocked, a read or write to the module generates a bus fault.
2:0	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.

Register 128: Run Mode Clock Gating Control Register 1 (RCGC1), offset 0x104


This register controls the clock gating logic in normal Run mode. Each bit controls a clock enable for a given interface, function, or module. If set, the module receives a clock and functions. Otherwise, the module is unclocked and disabled (saving power). If the module is unclocked, reads or writes to the module generate a bus fault. The reset state of these bits is 0 (unclocked) unless otherwise noted, so that all functional modules are disabled. It is the responsibility of software to enable the ports necessary for the application. Note that these registers may contain more bits than there are interfaces, functions, or modules to control. This configuration is implemented to assure reasonable code compatibility with other family and future parts. **RCGC1** is the clock configuration register for running operation, **SCGC1** for Sleep operation, and **DCGC1** for Deep-Sleep operation. Setting the ACG bit in the **Run-Mode Clock Configuration (RCC)** register specifies that the system uses sleep modes. Note that there must be a delay of 3 system clocks after a module clock is enabled before any registers in that module are accessed.

Important: This register is provided for legacy software support only.

The peripheral-specific Run Mode Clock Gating Control registers (such as **RCGCTIMER**) should be used to reset specific peripherals. A write to this legacy register also writes the corresponding bit in the peripheral-specific register. Any bits that are changed by writing to this register can be read back correctly with a read of this register. Software must use the peripheral-specific registers to support modules that are not present in the legacy registers. If software uses a peripheral-specific register to write a legacy peripheral (such as Timer 0), the write causes proper operation, but the value of that bit is not reflected in this register. If software uses both legacy and peripheral-specific register accesses, the peripheral-specific registers must be accessed by read-modify-write operations that affect only peripherals that are not present in the legacy registers. In this manner, both the peripheral-specific and legacy registers have coherent information.

Run Mode Clock Gating Control Register 1 (RCGC1)

Base 0x400F.E000 Offset 0x104 Type RO, reset 0x0000.0000



Bit/Field	Name	Туре	Reset	Description
26	COMP2	RO	0x0	Analog Comparator 2 Clock Gating This bit controls the clock gating for analog comparator 2. If set, the module receives a clock and functions. Otherwise, the module is unclocked and disabled. If the module is unclocked, a read or write to the module generates a bus fault.
25	COMP1	RO	0x0	Analog Comparator 1 Clock Gating This bit controls the clock gating for analog comparator 1. If set, the module receives a clock and functions. Otherwise, the module is unclocked and disabled. If the module is unclocked, a read or write to the module generates a bus fault.
24	COMP0	RO	0x0	Analog Comparator 0 Clock Gating This bit controls the clock gating for analog comparator 0. If set, the module receives a clock and functions. Otherwise, the module is unclocked and disabled. If the module is unclocked, a read or write to the module generates a bus fault.
23:20	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
19	TIMER3	RO	0x0	Timer 3 Clock Gating Control This bit controls the clock gating for General-Purpose Timer module 3. If set, the module receives a clock and functions. Otherwise, the module is unclocked and disabled. If the module is unclocked, a read or write to the module generates a bus fault.
18	TIMER2	RO	0x0	Timer 2 Clock Gating Control This bit controls the clock gating for General-Purpose Timer module 2. If set, the module receives a clock and functions. Otherwise, the module is unclocked and disabled. If the module is unclocked, a read or write to the module generates a bus fault.
17	TIMER1	RO	0x0	Timer 1 Clock Gating Control This bit controls the clock gating for General-Purpose Timer module 1. If set, the module receives a clock and functions. Otherwise, the module is unclocked and disabled. If the module is unclocked, a read or write to the module generates a bus fault.
16	TIMER0	RO	0x0	Timer 0 Clock Gating Control This bit controls the clock gating for General-Purpose Timer module 0. If set, the module receives a clock and functions. Otherwise, the module is unclocked and disabled. If the module is unclocked, a read or write to the module generates a bus fault.
15	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
14	I2C1	RO	0x0	I2C1 Clock Gating Control This bit controls the clock gating for I2C module 1. If set, the module receives a clock and functions. Otherwise, the module is unclocked and disabled. If the module is unclocked, a read or write to the module generates a bus fault.

Bit/Field	Name	Туре	Reset	Description
13	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
12	I2C0	RO	0x0	I2C0 Clock Gating Control
				This bit controls the clock gating for I2C module 0. If set, the module receives a clock and functions. Otherwise, the module is unclocked and disabled. If the module is unclocked, a read or write to the module generates a bus fault.
11:10	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
9	QEI1	RO	0x0	QEI1 Clock Gating Control
				This bit controls the clock gating for QEI module 1. If set, the module receives a clock and functions. Otherwise, the module is unclocked and disabled. If the module is unclocked, a read or write to the module generates a bus fault.
8	QEI0	RO	0x0	QEI0 Clock Gating Control
				This bit controls the clock gating for QEI module 0. If set, the module receives a clock and functions. Otherwise, the module is unclocked and disabled. If the module is unclocked, a read or write to the module generates a bus fault.
7:6	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
5	SSI1	RO	0x0	SSI1 Clock Gating Control
				This bit controls the clock gating for SSI module 1. If set, the module receives a clock and functions. Otherwise, the module is unclocked and disabled. If the module is unclocked, a read or write to the module generates a bus fault.
4	SSI0	RO	0x0	SSI0 Clock Gating Control
				This bit controls the clock gating for SSI module 0. If set, the module receives a clock and functions. Otherwise, the module is unclocked and disabled. If the module is unclocked, a read or write to the module generates a bus fault.
3	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
2	UART2	RO	0x0	UART2 Clock Gating Control
				This bit controls the clock gating for UART module 2. If set, the module receives a clock and functions. Otherwise, the module is unclocked and disabled. If the module is unclocked, a read or write to the module generates a bus fault.
1	UART1	RO	0x0	UART1 Clock Gating Control
				This bit controls the clock gating for UART module 1. If set, the module receives a clock and functions. Otherwise, the module is unclocked and disabled. If the module is unclocked, a read or write to the module generates a bus fault.

Bit/Field	Name	Туре	Reset	Description
0	UART0	RO	0x0	UART0 Clock Gating Control
				This bit controls the clock gating for UART module 0. If set, the module receives a clock and functions. Otherwise, the module is unclocked and disabled. If the module is unclocked, a read or write to the module generates a bus fault.

Register 129: Run Mode Clock Gating Control Register 2 (RCGC2), offset 0x108

This register controls the clock gating logic in normal Run mode. Each bit controls a clock enable for a given interface, function, or module. If set, the module receives a clock and functions. Otherwise, the module is unclocked and disabled (saving power). If the module is unclocked, reads or writes to the module generate a bus fault. The reset state of these bits is 0 (unclocked) unless otherwise noted, so that all functional modules are disabled. It is the responsibility of software to enable the ports necessary for the application. Note that these registers may contain more bits than there are interfaces, functions, or modules to control. This configuration is implemented to assure reasonable code compatibility with other family and future parts. **RCGC2** is the clock configuration register for running operation, **SCGC2** for Sleep operation, and **DCGC2** for Deep-Sleep operation. Setting the ACG bit in the **Run-Mode Clock Configuration (RCC)** register specifies that the system uses sleep modes. Note that there must be a delay of 3 system clocks after a module clock is enabled before any registers in that module are accessed.


Important: This register is provided for legacy software support only.

The peripheral-specific Run Mode Clock Gating Control registers (such as **RCGCDMA**) should be used to reset specific peripherals. A write to this legacy register also writes the corresponding bit in the peripheral-specific register. Any bits that are changed by writing to this register can be read back correctly with a read of this register. Software must use the peripheral-specific registers to support modules that are not present in the legacy registers. If software uses a peripheral-specific register to write a legacy peripheral (such as the μ DMA), the write causes proper operation, but the value of that bit is not reflected in this register. If software uses both legacy and peripheral-specific register accesses, the peripheral-specific registers must be accessed by read-modify-write operations that affect only peripherals that are not present in the legacy registers. In this manner, both the peripheral-specific and legacy registers have coherent information.

preserved across a read-modify-write operation.

Run Mode Clock Gating Control Register 2 (RCGC2)

Base 0x400F.E000 Offset 0x108 Type RO, reset 0x0000.0000



Bit/Field	Name	Туре	Reset	Description
16	USB0	RO	0x0	USB0 Clock Gating Control This bit controls the clock gating for USB module 0. If set, the module receives a clock and functions. Otherwise, the module is unclocked and disabled. If the module is unclocked, a read or write to the module generates a bus fault.
15:14	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
13	UDMA	RO	0x0	Micro-DMA Clock Gating Control This bit controls the clock gating for micro-DMA. If set, the module receives a clock and functions. Otherwise, the module is unclocked and disabled. If the module is unclocked, a read or write to the module generates a bus fault.
12:9	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
8	GPIOJ	RO	0x0	Port J Clock Gating Control
				This bit controls the clock gating for Port J. If set, the module receives a clock and functions. Otherwise, the module is unclocked and disabled. If the module is unclocked, a read or write to the module generates a bus fault.
7	GPIOH	RO	0x0	Port H Clock Gating Control
				This bit controls the clock gating for Port H. If set, the module receives a clock and functions. Otherwise, the module is unclocked and disabled. If the module is unclocked, a read or write to the module generates a bus fault.
6	GPIOG	RO	0x0	Port G Clock Gating Control
				This bit controls the clock gating for Port G. If set, the module receives a clock and functions. Otherwise, the module is unclocked and disabled. If the module is unclocked, a read or write to the module generates a bus fault.
5	GPIOF	RO	0x0	Port F Clock Gating Control
				This bit controls the clock gating for Port F. If set, the module receives a clock and functions. Otherwise, the module is unclocked and disabled. If the module is unclocked, a read or write to the module generates a bus fault.
4	GPIOE	RO	0x0	Port E Clock Gating Control
				Port E Clock Gating Control. This bit controls the clock gating for Port E. If set, the module receives a clock and functions. Otherwise, the module is unclocked and disabled. If the module is unclocked, a read or write to the module generates a bus fault.
3	GPIOD	RO	0x0	Port D Clock Gating Control
				Port D Clock Gating Control. This bit controls the clock gating for Port D. If set, the module receives a clock and functions. Otherwise, the module is unclocked and disabled. If the module is unclocked, a read or write to the module generates a bus fault.

Bit/Field	Name	Туре	Reset	Description
2	GPIOC	RO	0x0	Port C Clock Gating Control This bit controls the clock gating for Port C. If set, the module receives a clock and functions. Otherwise, the module is unclocked and disabled. If the module is unclocked, a read or write to the module generates a bus fault.
1	GPIOB	RO	0x0	Port B Clock Gating Control This bit controls the clock gating for Port B. If set, the module receives a clock and functions. Otherwise, the module is unclocked and disabled. If the module is unclocked, a read or write to the module generates a bus fault.
0	GPIOA	RO	0x0	Port A Clock Gating Control This bit controls the clock gating for Port A. If set, the module receives a clock and functions. Otherwise, the module is unclocked and disabled. If the module is unclocked, a read or write to the module generates a bus fault.

Register 130: Sleep Mode Clock Gating Control Register 0 (SCGC0), offset 0x110

This register controls the clock gating logic in Sleep mode. Each bit controls a clock enable for a given interface, function, or module. If set, the module receives a clock and functions. Otherwise, the module is unclocked and disabled (saving power). If the module is unclocked, reads or writes to the module generate a bus fault. The reset state of these bits is 0 (unclocked) unless otherwise noted, so that all functional modules are disabled. It is the responsibility of software to enable the ports necessary for the application. Note that these registers may contain more bits than there are interfaces, functions, or modules to control. This configuration is implemented to assure reasonable code compatibility with other family and future parts. **RCGC0** is the clock configuration register for running operation, **SCGC0** for Sleep operation, and **DCGC0** for Deep-Sleep operation. Setting the ACG bit in the **Run-Mode Clock Configuration (RCC)** register specifies that the system uses sleep modes.

Important: This register is provided for legacy software support only.

The peripheral-specific Sleep Mode Clock Gating Control registers (such as **SCGCWD**) should be used to reset specific peripherals. A write to this legacy register also writes the corresponding bit in the peripheral-specific register. Any bits that are changed by writing to this register can be read back correctly with a read of this register. Software must use the peripheral-specific registers to support modules that are not present in the legacy registers. If software uses a peripheral-specific register to write a legacy peripheral (such as Watchdog 1), the write causes proper operation, but the value of that bit is not reflected in this register. If software uses both legacy and peripheral-specific register accesses, the peripheral-specific registers must be accessed by read-modify-write operations that affect only peripherals that are not present in the legacy registers. In this manner, both the peripheral-specific and legacy registers have coherent information.

Sleep Mode Clock Gating Control Register 0 (SCGC0)

WDT1

RO

0x0

Base 0x400F.E000 Offset 0x110 Type RO, reset 0x0000.0040

28

	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16
		reserved		WDT1	rese	ved	CAN1	CAN0		reserved		PWM0	rese	rved	ADC1	ADC0
Туре	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO
Reset	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0
	15	14	13	12	11	10	9	8	7	6	5	4	3	2	1	0
					reserved					HIB	rese	rved	WDT0		reserved	
Type	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO
Reset	0	0	0	0	0	0	0	0	0	1	0	0	0	0	0	0
	Bit/Field 31:29		Nam		Ty _l		Reset 0	Soft com	patibility	ould not of the court of the co	ıre prod	ucts, the	value of	a reserv		
								pies	erveu a	C1033 a 1	cau-moc	any-wine	operation)II.		

WDT1 Clock Gating Control

the module generates a bus fault.

This bit controls the clock gating for Watchdog Timer module 1. If set, the module receives a clock and functions. Otherwise, the module is unclocked and disabled. If the module is unclocked, a read or write to

Bit/Field	Name	Туре	Reset	Description
27:26	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
25	CAN1	RO	0x0	CAN1 Clock Gating Control
				This bit controls the clock gating for CAN module 1. If set, the module receives a clock and functions. Otherwise, the module is unclocked and disabled. If the module is unclocked, a read or write to the module generates a bus fault.
24	CAN0	RO	0x0	CAN0 Clock Gating Control
				This bit controls the clock gating for CAN module 0. If set, the module receives a clock and functions. Otherwise, the module is unclocked and disabled. If the module is unclocked, a read or write to the module generates a bus fault.
23:21	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
20	PWM0	RO	0x0	PWM Clock Gating Control
				This bit controls the clock gating for the PWM module. If set, the module receives a clock and functions. Otherwise, the module is unclocked and disabled. If the module is unclocked, a read or write to the module generates a bus fault.
19:18	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
17	ADC1	RO	0x0	ADC1 Clock Gating Control
				This bit controls the clock gating for ADC module 1. If set, the module receives a clock and functions. Otherwise, the module is unclocked and disabled. If the module is unclocked, a read or write to the module generates a bus fault.
16	ADC0	RO	0x0	ADC0 Clock Gating Control
				This bit controls the clock gating for ADC module 0. If set, the module receives a clock and functions. Otherwise, the module is unclocked and disabled. If the module is unclocked, a read or write to the module generates a bus fault.
15:7	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
6	HIB	RO	0x1	HIB Clock Gating Control
				This bit controls the clock gating for the Hibernation module. If set, the module receives a clock and functions. Otherwise, the module is unclocked and disabled. If the module is unclocked, a read or write to the module generates a bus fault.
5:4	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.

Bit/Field	Name	Туре	Reset	Description
3	WDT0	RO	0x0	WDT0 Clock Gating Control This bit controls the clock gating for the Watchdog Timer module 0. If set, the module receives a clock and functions. Otherwise, the module is unclocked and disabled. If the module is unclocked, a read or write to the module generates a bus fault.
2:0	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.

Register 131: Sleep Mode Clock Gating Control Register 1 (SCGC1), offset 0x114

This register controls the clock gating logic in Sleep mode. Each bit controls a clock enable for a given interface, function, or module. If set, the module receives a clock and functions. Otherwise, the module is unclocked and disabled (saving power). If the module is unclocked, reads or writes to the module generate a bus fault. The reset state of these bits is 0 (unclocked) unless otherwise noted, so that all functional modules are disabled. It is the responsibility of software to enable the ports necessary for the application. Note that these registers may contain more bits than there are interfaces, functions, or modules to control. This configuration is implemented to assure reasonable code compatibility with other family and future parts. RCGC1 is the clock configuration register for running operation, SCGC1 for Sleep operation, and DCGC1 for Deep-Sleep operation. Setting the ACG bit in the Run-Mode Clock Configuration (RCC) register specifies that the system uses sleep modes.

Important: This register is provided for legacy software support only.

The peripheral-specific Sleep Mode Clock Gating Control registers (such as **SCGCTIMER**) should be used to reset specific peripherals. A write to this legacy register also writes the corresponding bit in the peripheral-specific register. Any bits that are changed by writing to this register can be read back correctly with a read of this register. Software must use the peripheral-specific registers to support modules that are not present in the legacy registers. If software uses a peripheral-specific register to write a legacy peripheral (such as Timer 0), the write causes proper operation, but the value of that bit is not reflected in this register. If software uses both legacy and peripheral-specific register accesses, the peripheral-specific registers must be accessed by read-modify-write operations that affect only peripherals that are not present in the legacy registers. In this manner, both the peripheral-specific and legacy registers have coherent information.

unclocked and disabled. If the module is unclocked, a read or write to

Sleep Mode Clock Gating Control Register 1 (SCGC1)

Base 0x400F.E000 Offset 0x114 Type RO, reset 0x0000.0000

	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16
	ľ		reserved			COMP2	COMP1	COMP0		rese	rved		TIMER3	TIMER2	TIMER1	TIMER0
Type Reset	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0
	15	14	13	12	11	10	9	8	7	6	5	4	3	2	1	0
	reserved	I2C1	reserved	I2C0	rese	rved	QEI1	QEI0	rese	rved	SSI1	SSI0	reserved	UART2	UART1	UART0
Type Reset	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0
E	Bit/Field		Nam	e	Ту	ре	Reset	Des	cription							
	31:27		reserv	ed .	R	0	0	com	ware should not rely on the value of a reserved bit. To provide patibility with future products, the value of a reserved bit should be berved across a read-modify-write operation.							
	26		COM	P2	R	0	0x0	Ana	log Com	parator 2	2 Clock (Gating				
											•	•	nalog co s. Otherv	•		-

the module generates a bus fault.

Bit/Field	Name	Туре	Reset	Description
25	COMP1	RO	0x0	Analog Comparator 1 Clock Gating This bit controls the clock gating for analog comparator 1. If set, the module receives a clock and functions. Otherwise, the module is unclocked and disabled. If the module is unclocked, a read or write to the module generates a bus fault.
24	COMP0	RO	0x0	Analog Comparator 0 Clock Gating This bit controls the clock gating for analog comparator 0. If set, the module receives a clock and functions. Otherwise, the module is unclocked and disabled. If the module is unclocked, a read or write to the module generates a bus fault.
23:20	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
19	TIMER3	RO	0x0	Timer 3 Clock Gating Control
				This bit controls the clock gating for General-Purpose Timer module 3. If set, the module receives a clock and functions. Otherwise, the module is unclocked and disabled. If the module is unclocked, a read or write to the module generates a bus fault.
18	TIMER2	RO	0x0	Timer 2 Clock Gating Control
				This bit controls the clock gating for General-Purpose Timer module 2. If set, the module receives a clock and functions. Otherwise, the module is unclocked and disabled. If the module is unclocked, a read or write to the module generates a bus fault.
17	TIMER1	RO	0x0	Timer 1 Clock Gating Control
				This bit controls the clock gating for General-Purpose Timer module 1. If set, the module receives a clock and functions. Otherwise, the module is unclocked and disabled. If the module is unclocked, a read or write to the module generates a bus fault.
16	TIMER0	RO	0x0	Timer 0 Clock Gating Control
				This bit controls the clock gating for General-Purpose Timer module 0. If set, the module receives a clock and functions. Otherwise, the module is unclocked and disabled. If the module is unclocked, a read or write to the module generates a bus fault.
15	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
14	I2C1	RO	0x0	I2C1 Clock Gating Control
				This bit controls the clock gating for I2C module 1. If set, the module receives a clock and functions. Otherwise, the module is unclocked and disabled. If the module is unclocked, a read or write to the module generates a bus fault.
13	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.

Bit/Field	Name	Туре	Reset	Description
12	I2C0	RO	0x0	I2C0 Clock Gating Control
				This bit controls the clock gating for I2C module 0. If set, the module receives a clock and functions. Otherwise, the module is unclocked and disabled. If the module is unclocked, a read or write to the module generates a bus fault.
11:10	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
9	QEI1	RO	0x0	QEI1 Clock Gating Control
				This bit controls the clock gating for QEI module 1. If set, the module receives a clock and functions. Otherwise, the module is unclocked and disabled. If the module is unclocked, a read or write to the module generates a bus fault.
8	QEI0	RO	0x0	QEI0 Clock Gating Control
				This bit controls the clock gating for QEI module 0. If set, the module receives a clock and functions. Otherwise, the module is unclocked and disabled. If the module is unclocked, a read or write to the module generates a bus fault.
7:6	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
5	SSI1	RO	0x0	SSI1 Clock Gating Control
				This bit controls the clock gating for SSI module 1. If set, the module receives a clock and functions. Otherwise, the module is unclocked and disabled. If the module is unclocked, a read or write to the module generates a bus fault.
4	SSI0	RO	0x0	SSI0 Clock Gating Control
				This bit controls the clock gating for SSI module 0. If set, the module receives a clock and functions. Otherwise, the module is unclocked and disabled. If the module is unclocked, a read or write to the module generates a bus fault.
3	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
2	UART2	RO	0x0	UART2 Clock Gating Control
				This bit controls the clock gating for UART module 2. If set, the module receives a clock and functions. Otherwise, the module is unclocked and disabled. If the module is unclocked, a read or write to the module generates a bus fault.
1	UART1	RO	0x0	UART1 Clock Gating Control
				This bit controls the clock gating for UART module 1. If set, the module receives a clock and functions. Otherwise, the module is unclocked and disabled. If the module is unclocked, a read or write to the module generates a bus fault.

Bit/Field	Name	Туре	Reset	Description
0	UART0	RO	0x0	UART0 Clock Gating Control
				This bit controls the clock gating for UART module 0. If set, the module receives a clock and functions. Otherwise, the module is unclocked and disabled. If the module is unclocked, a read or write to the module generates a bus fault.

Register 132: Sleep Mode Clock Gating Control Register 2 (SCGC2), offset 0x118


This register controls the clock gating logic in Sleep mode. Each bit controls a clock enable for a given interface, function, or module. If set, the module receives a clock and functions. Otherwise, the module is unclocked and disabled (saving power). If the module is unclocked, reads or writes to the module generate a bus fault. The reset state of these bits is 0 (unclocked) unless otherwise noted, so that all functional modules are disabled. It is the responsibility of software to enable the ports necessary for the application. Note that these registers may contain more bits than there are interfaces, functions, or modules to control. This configuration is implemented to assure reasonable code compatibility with other family and future parts. **RCGC2** is the clock configuration register for running operation, **SCGC2** for Sleep operation, and **DCGC2** for Deep-Sleep operation. Setting the ACG bit in the **Run-Mode Clock Configuration (RCC)** register specifies that the system uses sleep modes.

Important: This register is provided for legacy software support only.

The peripheral-specific Sleep Mode Clock Gating Control registers (such as SCGCDMA) should be used to reset specific peripherals. A write to this legacy register also writes the corresponding bit in the peripheral-specific register. Any bits that are changed by writing to this register can be read back correctly with a read of this register. Software must use the peripheral-specific registers to support modules that are not present in the legacy registers. If software uses a peripheral-specific register to write a legacy peripheral (such as the μDMA), the write causes proper operation, but the value of that bit is not reflected in this register. If software uses both legacy and peripheral-specific register accesses, the peripheral-specific registers must be accessed by read-modify-write operations that affect only peripherals that are not present in the legacy registers. In this manner, both the peripheral-specific and legacy registers have coherent information.

Sleep Mode Clock Gating Control Register 2 (SCGC2)

Base 0x400F.E000 Offset 0x118 Type RO, reset 0x0000.0000



Bit/Field	Name	Type	Reset	Description
31:17	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
16	USB0	RO	0x0	USB0 Clock Gating Control

This bit controls the clock gating for USB module 0. If set, the module receives a clock and functions. Otherwise, the module is unclocked and disabled. If the module is unclocked, a read or write to the module generates a bus fault.

Bit/Field	Name	Туре	Reset	Description
15:14	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
13	UDMA	RO	0x0	Micro-DMA Clock Gating Control
				This bit controls the clock gating for micro-DMA. If set, the module receives a clock and functions. Otherwise, the module is unclocked and disabled. If the module is unclocked, a read or write to the module generates a bus fault.
12:9	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
8	GPIOJ	RO	0x0	Port J Clock Gating Control
				This bit controls the clock gating for Port J. If set, the module receives a clock and functions. Otherwise, the module is unclocked and disabled. If the module is unclocked, a read or write to the module generates a bus fault.
7	GPIOH	RO	0x0	Port H Clock Gating Control
				This bit controls the clock gating for Port H. If set, the module receives a clock and functions. Otherwise, the module is unclocked and disabled. If the module is unclocked, a read or write to the module generates a bus fault.
6	GPIOG	RO	0x0	Port G Clock Gating Control
				This bit controls the clock gating for Port G. If set, the module receives a clock and functions. Otherwise, the module is unclocked and disabled. If the module is unclocked, a read or write to the module generates a bus fault.
5	GPIOF	RO	0x0	Port F Clock Gating Control
				This bit controls the clock gating for Port F. If set, the module receives a clock and functions. Otherwise, the module is unclocked and disabled. If the module is unclocked, a read or write to the module generates a bus fault.
4	GPIOE	RO	0x0	Port E Clock Gating Control
				Port E Clock Gating Control. This bit controls the clock gating for Port E. If set, the module receives a clock and functions. Otherwise, the module is unclocked and disabled. If the module is unclocked, a read or write to the module generates a bus fault.
3	GPIOD	RO	0x0	Port D Clock Gating Control
				Port D Clock Gating Control. This bit controls the clock gating for Port D. If set, the module receives a clock and functions. Otherwise, the module is unclocked and disabled. If the module is unclocked, a read or write to the module generates a bus fault.
2	GPIOC	RO	0x0	Port C Clock Gating Control
				This bit controls the clock gating for Port C. If set, the module receives a clock and functions. Otherwise, the module is unclocked and disabled. If the module is unclocked, a read or write to the module generates a bus fault.

Bit/Field	Name	Type	Reset	Description
1	GPIOB	RO	0x0	Port B Clock Gating Control This bit controls the clock gating for Port B. If set, the module receives a clock and functions. Otherwise, the module is unclocked and disabled. If the module is unclocked, a read or write to the module generates a bus fault.
0	GPIOA	RO	0x0	Port A Clock Gating Control This bit controls the clock gating for Port A. If set, the module receives a clock and functions. Otherwise, the module is unclocked and disabled. If the module is unclocked, a read or write to the module generates a bus fault.

Register 133: Deep Sleep Mode Clock Gating Control Register 0 (DCGC0), offset 0x120


This register controls the clock gating logic in Deep-Sleep mode. Each bit controls a clock enable for a given interface, function, or module. If set, the module receives a clock and functions. Otherwise, the module is unclocked and disabled (saving power). If the module is unclocked, reads or writes to the module generate a bus fault. The reset state of these bits is 0 (unclocked) unless otherwise noted, so that all functional modules are disabled. It is the responsibility of software to enable the ports necessary for the application. Note that these registers may contain more bits than there are interfaces, functions, or modules to control. This configuration is implemented to assure reasonable code compatibility with other family and future parts. **RCGC0** is the clock configuration register for running operation, **SCGC0** for Sleep operation, and **DCGC0** for Deep-Sleep operation. Setting the ACG bit in the **Run-Mode Clock Configuration (RCC)** register specifies that the system uses sleep modes.

Important: This register is provided for legacy software support only.

The peripheral-specific Deep Sleep Mode Clock Gating Control registers (such as **DCGCWD**) should be used to reset specific peripherals. A write to this legacy register also writes the corresponding bit in the peripheral-specific register. Any bits that are changed by writing to this register can be read back correctly with a read of this register. Software must use the peripheral-specific registers to support modules that are not present in the legacy registers. If software uses a peripheral-specific register to write a legacy peripheral (such as Watchdog 1), the write causes proper operation, but the value of that bit is not reflected in this register. If software uses both legacy and peripheral-specific register accesses, the peripheral-specific registers must be accessed by read-modify-write operations that affect only peripherals that are not present in the legacy registers. In this manner, both the peripheral-specific and legacy registers have coherent information.

Deep Sleep Mode Clock Gating Control Register 0 (DCGC0)

Base 0x400F.E000 Offset 0x120 Type RO, reset 0x0000.0040



set, the module receives a clock and functions. Otherwise, the module is unclocked and disabled. If the module is unclocked, a read or write

to the module generates a bus fault.

Bit/Field	Name	Туре	Reset	Description
27:26	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
25	CAN1	RO	0x0	CAN1 Clock Gating Control
				This bit controls the clock gating for CAN module 1. If set, the module receives a clock and functions. Otherwise, the module is unclocked and disabled. If the module is unclocked, a read or write to the module generates a bus fault.
24	CAN0	RO	0x0	CAN0 Clock Gating Control
				This bit controls the clock gating for CAN module 0. If set, the module receives a clock and functions. Otherwise, the module is unclocked and disabled. If the module is unclocked, a read or write to the module generates a bus fault.
23:21	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
20	PWM0	RO	0x0	PWM Clock Gating Control
				This bit controls the clock gating for the PWM module. If set, the module receives a clock and functions. Otherwise, the module is unclocked and disabled. If the module is unclocked, a read or write to the module generates a bus fault.
19:18	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
17	ADC1	RO	0x0	ADC1 Clock Gating Control
				This bit controls the clock gating for ADC module 1. If set, the module receives a clock and functions. Otherwise, the module is unclocked and disabled. If the module is unclocked, a read or write to the module generates a bus fault.
16	ADC0	RO	0x0	ADC0 Clock Gating Control
				This bit controls the clock gating for ADC module 0. If set, the module receives a clock and functions. Otherwise, the module is unclocked and disabled. If the module is unclocked, a read or write to the module generates a bus fault.
15:7	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
6	HIB	RO	0x1	HIB Clock Gating Control
				This bit controls the clock gating for the Hibernation module. If set, the module receives a clock and functions. Otherwise, the module is unclocked and disabled. If the module is unclocked, a read or write to the module generates a bus fault.
5:4	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.

Bit/Field	Name	Туре	Reset	Description				
3	WDT0	RO	0x0	WDT0 Clock Gating Control This bit controls the clock gating for the Watchdog Timer module 0. If set, the module receives a clock and functions. Otherwise, the module is unclocked and disabled. If the module is unclocked, a read or write to the module generates a bus fault.				
2:0	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.				

16

Register 134: Deep-Sleep Mode Clock Gating Control Register 1 (DCGC1), offset 0x124

This register controls the clock gating logic in Deep-Sleep mode. Each bit controls a clock enable for a given interface, function, or module. If set, the module receives a clock and functions. Otherwise, the module is unclocked and disabled (saving power). If the module is unclocked, reads or writes to the module generate a bus fault. The reset state of these bits is 0 (unclocked) unless otherwise noted, so that all functional modules are disabled. It is the responsibility of software to enable the ports necessary for the application. Note that these registers may contain more bits than there are interfaces, functions, or modules to control. This configuration is implemented to assure reasonable code compatibility with other family and future parts. **RCGC1** is the clock configuration register for running operation, **SCGC1** for Sleep operation, and **DCGC1** for Deep-Sleep operation. Setting the ACG bit in the **Run-Mode Clock Configuration (RCC)** register specifies that the system uses sleep modes.

Important: This register is provided for legacy software support only.

The peripheral-specific Deep Sleep Mode Clock Gating Control registers (such as **DCGCTIMER**) should be used to reset specific peripherals. A write to this legacy register also writes the corresponding bit in the peripheral-specific register. Any bits that are changed by writing to this register can be read back correctly with a read of this register. Software must use the peripheral-specific registers to support modules that are not present in the legacy registers. If software uses a peripheral-specific register to write a legacy peripheral (such as Timer 0), the write causes proper operation, but the value of that bit is not reflected in this register. If software uses both legacy and peripheral-specific register accesses, the peripheral-specific registers must be accessed by read-modify-write operations that affect only peripherals that are not present in the legacy registers. In this manner, both the peripheral-specific and legacy registers have coherent information.

module receives a clock and functions. Otherwise, the module is unclocked and disabled. If the module is unclocked, a read or write to

the module generates a bus fault.

Deep-Sleep Mode Clock Gating Control Register 1 (DCGC1)

Base 0x400F.E000 Offset 0x124 Type RO, reset 0x0000.0000

	31	30	29	28	21	26	25	24	23	22	21	20	19	18	17	16
			reserved			COMP2	COMP1	COMP0		rese	rved		TIMER3	TIMER2	TIMER1	TIMER0
Type	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO
Reset	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0
	15	14	13	12	11	10	9	8	7	6	5	4	3	2	1	0
	reserved	I2C1	reserved	I2C0	rese	rved	QEI1	QEI0	rese	rved	SSI1	SSI0	reserved	UART2	UART1	UART0
Туре	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO
Reset	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0
E	Bit/Field		Nam	e	Ту	ре	Reset	Des	cription							
	31:27		reserv	red	R	0	0	com	patibility	with futu	ıre prodi	ucts, the	of a reservatue of operation	a reserv	•	
	26		COM	P2	R	0	0x0	Ana	log Com	parator 2	2 Clock (Gating				
							This	This bit controls the clock gating for analog comparator 2. If set, the								

Bit/Field	Name	Туре	Reset	Description
25	COMP1	RO	0x0	Analog Comparator 1 Clock Gating This bit controls the clock gating for analog comparator 1. If set, the module receives a clock and functions. Otherwise, the module is unclocked and disabled. If the module is unclocked, a read or write to the module generates a bus fault.
24	COMP0	RO	0x0	Analog Comparator 0 Clock Gating This bit controls the clock gating for analog comparator 0. If set, the module receives a clock and functions. Otherwise, the module is unclocked and disabled. If the module is unclocked, a read or write to the module generates a bus fault.
23:20	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
19	TIMER3	RO	0x0	Timer 3 Clock Gating Control This bit controls the clock gating for General-Purpose Timer module 3. If set, the module receives a clock and functions. Otherwise, the module is unclocked and disabled. If the module is unclocked, a read or write to the module generates a bus fault.
18	TIMER2	RO	0x0	Timer 2 Clock Gating Control This bit controls the clock gating for General-Purpose Timer module 2. If set, the module receives a clock and functions. Otherwise, the module is unclocked and disabled. If the module is unclocked, a read or write to the module generates a bus fault.
17	TIMER1	RO	0x0	Timer 1 Clock Gating Control This bit controls the clock gating for General-Purpose Timer module 1. If set, the module receives a clock and functions. Otherwise, the module is unclocked and disabled. If the module is unclocked, a read or write to the module generates a bus fault.
16	TIMERO	RO	0x0	Timer 0 Clock Gating Control This bit controls the clock gating for General-Purpose Timer module 0. If set, the module receives a clock and functions. Otherwise, the module is unclocked and disabled. If the module is unclocked, a read or write to the module generates a bus fault.
15	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
14	I2C1	RO	0x0	I2C1 Clock Gating Control This bit controls the clock gating for I2C module 1. If set, the module receives a clock and functions. Otherwise, the module is unclocked and disabled. If the module is unclocked, a read or write to the module generates a bus fault.
13	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.

Bit/Field	Name	Туре	Reset	Description
12	I2C0	RO	0x0	I2C0 Clock Gating Control
				This bit controls the clock gating for I2C module 0. If set, the module receives a clock and functions. Otherwise, the module is unclocked and disabled. If the module is unclocked, a read or write to the module generates a bus fault.
11:10	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
9	QEI1	RO	0x0	QEI1 Clock Gating Control
				This bit controls the clock gating for QEI module 1. If set, the module receives a clock and functions. Otherwise, the module is unclocked and disabled. If the module is unclocked, a read or write to the module generates a bus fault.
8	QEI0	RO	0x0	QEI0 Clock Gating Control
				This bit controls the clock gating for QEI module 0. If set, the module receives a clock and functions. Otherwise, the module is unclocked and disabled. If the module is unclocked, a read or write to the module generates a bus fault.
7:6	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
5	SSI1	RO	0x0	SSI1 Clock Gating Control
				This bit controls the clock gating for SSI module 1. If set, the module receives a clock and functions. Otherwise, the module is unclocked and disabled. If the module is unclocked, a read or write to the module generates a bus fault.
4	SSI0	RO	0x0	SSI0 Clock Gating Control
				This bit controls the clock gating for SSI module 0. If set, the module receives a clock and functions. Otherwise, the module is unclocked and disabled. If the module is unclocked, a read or write to the module generates a bus fault.
3	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
2	UART2	RO	0x0	UART2 Clock Gating Control
				This bit controls the clock gating for UART module 2. If set, the module receives a clock and functions. Otherwise, the module is unclocked and disabled. If the module is unclocked, a read or write to the module generates a bus fault.
1	UART1	RO	0x0	UART1 Clock Gating Control
				This bit controls the clock gating for UART module 1. If set, the module receives a clock and functions. Otherwise, the module is unclocked and disabled. If the module is unclocked, a read or write to the module generates a bus fault.

Bit/Field	Name	Туре	Reset	Description
0	UART0	RO	0x0	UART0 Clock Gating Control
				This bit controls the clock gating for UART module 0. If set, the module receives a clock and functions. Otherwise, the module is unclocked and disabled. If the module is unclocked, a read or write to the module generates a bus fault.

Register 135: Deep Sleep Mode Clock Gating Control Register 2 (DCGC2), offset 0x128


This register controls the clock gating logic in Deep-Sleep mode. Each bit controls a clock enable for a given interface, function, or module. If set, the module receives a clock and functions. Otherwise, the module is unclocked and disabled (saving power). If the module is unclocked, reads or writes to the module generate a bus fault. The reset state of these bits is 0 (unclocked) unless otherwise noted, so that all functional modules are disabled. It is the responsibility of software to enable the ports necessary for the application. Note that these registers may contain more bits than there are interfaces, functions, or modules to control. This configuration is implemented to assure reasonable code compatibility with other family and future parts. **RCGC2** is the clock configuration register for running operation, **SCGC2** for Sleep operation, and **DCGC2** for Deep-Sleep operation. Setting the ACG bit in the **Run-Mode Clock Configuration (RCC)** register specifies that the system uses sleep modes.

Important: This register is provided for legacy software support only.

The peripheral-specific Deep Sleep Mode Clock Gating Control registers (such as DCGCDMA) should be used to reset specific peripherals. A write to this legacy register also writes the corresponding bit in the peripheral-specific register. Any bits that are changed by writing to this register can be read back correctly with a read of this register. Software must use the peripheral-specific registers to support modules that are not present in the legacy registers. If software uses a peripheral-specific register to write a legacy peripheral (such as the $\mu\text{DMA})$, the write causes proper operation, but the value of that bit is not reflected in this register. If software uses both legacy and peripheral-specific register accesses, the peripheral-specific registers must be accessed by read-modify-write operations that affect only peripherals that are not present in the legacy registers. In this manner, both the peripheral-specific and legacy registers have coherent information.

Deep Sleep Mode Clock Gating Control Register 2 (DCGC2)

Base 0x400F.E000 Offset 0x128 Type RO, reset 0x0000.0000



Bit/Field	Name	Туре	Reset	Description
31:17	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
16	USB0	RO	0x0	USB0 Clock Gating Control

This bit controls the clock gating for USB module 0. If set, the module receives a clock and functions. Otherwise, the module is unclocked and disabled. If the module is unclocked, a read or write to the module generates a bus fault.

Bit/Field	Name	Туре	Reset	Description
15:14	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
13	UDMA	RO	0x0	Micro-DMA Clock Gating Control
				This bit controls the clock gating for micro-DMA. If set, the module receives a clock and functions. Otherwise, the module is unclocked and disabled. If the module is unclocked, a read or write to the module generates a bus fault.
12:9	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
8	GPIOJ	RO	0x0	Port J Clock Gating Control
				This bit controls the clock gating for Port J. If set, the module receives a clock and functions. Otherwise, the module is unclocked and disabled. If the module is unclocked, a read or write to the module generates a bus fault.
7	GPIOH	RO	0x0	Port H Clock Gating Control
				This bit controls the clock gating for Port H. If set, the module receives a clock and functions. Otherwise, the module is unclocked and disabled. If the module is unclocked, a read or write to the module generates a bus fault.
6	GPIOG	RO	0x0	Port G Clock Gating Control
				This bit controls the clock gating for Port G. If set, the module receives a clock and functions. Otherwise, the module is unclocked and disabled. If the module is unclocked, a read or write to the module generates a bus fault.
5	GPIOF	RO	0x0	Port F Clock Gating Control
				This bit controls the clock gating for Port F. If set, the module receives a clock and functions. Otherwise, the module is unclocked and disabled. If the module is unclocked, a read or write to the module generates a bus fault.
4	GPIOE	RO	0x0	Port E Clock Gating Control
				Port E Clock Gating Control. This bit controls the clock gating for Port E. If set, the module receives a clock and functions. Otherwise, the module is unclocked and disabled. If the module is unclocked, a read or write to the module generates a bus fault.
3	GPIOD	RO	0x0	Port D Clock Gating Control
				Port D Clock Gating Control. This bit controls the clock gating for Port D. If set, the module receives a clock and functions. Otherwise, the module is unclocked and disabled. If the module is unclocked, a read or write to the module generates a bus fault.
2	GPIOC	RO	0x0	Port C Clock Gating Control
				This bit controls the clock gating for Port C. If set, the module receives a clock and functions. Otherwise, the module is unclocked and disabled. If the module is unclocked, a read or write to the module generates a bus fault.

Bit/Field	Name	Туре	Reset	Description
1	GPIOB	RO	0x0	Port B Clock Gating Control This bit controls the clock gating for Port B. If set, the module receives a clock and functions. Otherwise, the module is unclocked and disabled. If the module is unclocked, a read or write to the module generates a bus fault.
0	GPIOA	RO	0x0	Port A Clock Gating Control This bit controls the clock gating for Port A. If set, the module receives a clock and functions. Otherwise, the module is unclocked and disabled. If the module is unclocked, a read or write to the module generates a bus fault.

Register 136: Device Capabilities 9 (DC9), offset 0x190

This register is predefined by the part and can be used to verify ADC digital comparator features.

Important: This register is provided for legacy software support only.

The **ADC Peripheral Properties (ADCPP)** register should be used to determine how many digital comparators are available on the ADC module. A read of this register correctly identifies if legacy comparators are present. Software must use the **ADCPP** register to determine if a comparator that is not supported by the **DCn** registers is present.

Device Capabilities 9 (DC9)

Base 0x400F.E000 Offset 0x190 Type RO, reset 0x00FF.00FF

_	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16
	'			rese	rved				ADC1DC7	ADC1DC6	ADC1DC5	ADC1DC4	ADC1DC3	ADC1DC2	ADC1DC1	ADC1DC0
Туре	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO
Reset	0	0	0	0	0	0	0	0	1	1	1	1	1	1	1	1
	15	14	13	12	11	10	9	8	7	6	5	4	3	2	1	0
				rese	rved				ADC0DC7	ADC0DC6	ADC0DC5	ADC0DC4	ADC0DC3	ADC0DC2	ADC0DC1	ADC0DC0
Туре	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO
Reset	0	0	0	0	0	0	0	0	1	1	1	1	1	1	1	1
Е	Bit/Field Name Type		Reset	Des	Description											
	31:24		reserv	/ed	R	0	0	con	tware she npatibility served a	with futu	ıre prod	ucts, the	value of	a reserv	•	
	23		ADC1	C1DC7 RO		0x1		ADC1 DC7 Present When set, indicates that ADC module 1 Digital Comparator 7 is present.								
	22		ADC1	DC6	RO		0x1		ADC1 DC6 Present When set, indicates that ADC module 1 Digital Comparator 6 is present.							
	21		ADC1	DC5	R	0	0x1		ADC1 DC5 Present When set, indicates that ADC module 1 Digital Comparator 5 is present.							
	20		ADC1	DC4	R	0	0x1		ADC1 DC4 Present When set, indicates that ADC module 1 Digital Comparator 4 is present							present.
	19		ADC1	DC3	R	0	0x1		ADC1 DC3 Present When set, indicates that ADC module 1 Digital Comparator 3 is prese							present.
	18		ADC1	DC2	R	0	0x1	ADC1 DC2 Present When set, indicates that ADC module 1 Digital Comparator 2 is pres							present.	
	17		ADC1	DC1	R	0	0x1		C1 DC1 I en set, in		hat ADC	module	1 Digital	Compar	ator 1 is	present.
	16		ADC1	DC0	R	0	0x1	AD	C1 DC0 I	Present						

When set, indicates that ADC module 1 Digital Comparator 0 is present.

Bit/Field	Name	Туре	Reset	Description
15:8	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
7	ADC0DC7	RO	0x1	ADC0 DC7 Present When set, indicates that ADC module 0 Digital Comparator 7 is present.
6	ADC0DC6	RO	0x1	ADC0 DC6 Present When set, indicates that ADC module 0 Digital Comparator 6 is present.
5	ADC0DC5	RO	0x1	ADC0 DC5 Present When set, indicates that ADC module 0 Digital Comparator 5 is present.
4	ADC0DC4	RO	0x1	ADC0 DC4 Present When set, indicates that ADC module 0 Digital Comparator 4 is present.
3	ADC0DC3	RO	0x1	ADC0 DC3 Present When set, indicates that ADC module 0 Digital Comparator 3 is present.
2	ADC0DC2	RO	0x1	ADC0 DC2 Present When set, indicates that ADC module 0 Digital Comparator 2 is present.
1	ADC0DC1	RO	0x1	ADC0 DC1 Present When set, indicates that ADC module 0 Digital Comparator 1 is present.
0	ADC0DC0	RO	0x1	ADC0 DC0 Present When set, indicates that ADC module 0 Digital Comparator 0 is present.

Register 137: Non-Volatile Memory Information (NVMSTAT), offset 0x1A0


This register is predefined by the part and can be used to verify features.

Important: This register is provided for legacy software support only.

The ROM Third-Party Software (ROMSWMAP) register should be used to determine the presence of third-party software in the on-chip ROM on this microcontroller. A read of the TPSW bit in this register correctly identifies the presence of legacy third-party software. Software should use the **ROMSWMAP** register for software that is not on legacy devices.

Non-Volatile Memory Information (NVMSTAT)

Base 0x400F.E000 Offset 0x1A0
Type RO, reset 0x0000.0001



Bit/Field	Name	Type	Reset	Description
31:1	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
0	FWB	RO	0x1	32 Word Flash Write Buffer Available

When set, indicates that the 32 word Flash memory write buffer feature is available.

6 System Exception Module

This module is an AHB peripheral that handles system-level Cortex-M4 FPU exceptions. For functions with registers mapped into this aperture, if the function is not available on a device, then all writes to the associated registers are ignored and reads return zeros.

6.1 Functional Description

The System Exception module provides control and status of the system-level interrupts. All the interrupt events are ORed together before being sent to the interrupt controller, so the System Exception module can only generate a single interrupt request to the controller at any given time. Software can service multiple interrupt events in a single interrupt service routine by reading the System Exception Masked Interrupt Status (SYSEXCMIS) register. The interrupt events that can trigger a controller-level interrupt are defined in the System Exception Interrupt Mask (SYSEXCIM) register by setting the corresponding interrupt mask bits. If interrupts are not used, the raw interrupt status is always visible via the System Exception Raw Interrupt Status (SYSEXCRIS) register. Interrupts are always cleared (for both the SYSEXCMIS and SYSEXCRIS registers) by writing a 1 to the corresponding bit in the System Exception Interrupt Clear (SYSEXCIC) register.

6.2 Register Map

Table 6-1 on page 483 lists the System Exception module registers. The offset listed is a hexadecimal increment to the register's address, relative to the System Exception base address of 0x400F.9000.

Note: Spaces in the System Exception register space that are not used are reserved for future or internal use. Software should not modify any reserved memory address.

Table 6-1. System Exception Register Map

Offset	Name	Туре	Reset	Description	See page
0x000	SYSEXCRIS	RO	0x0000.0000	System Exception Raw Interrupt Status	484
0x004	SYSEXCIM	R/W	0x0000.0000	System Exception Interrupt Mask	486
0x008	SYSEXCMIS	RO	0x0000.0000	System Exception Masked Interrupt Status	488
0x00C	SYSEXCIC	W1C	0x0000.0000	System Exception Interrupt Clear	490

6.3 Register Descriptions


All addresses given are relative to the System Exception base address of 0x400F.9000.

Register 1: System Exception Raw Interrupt Status (SYSEXCRIS), offset 0x000

The SYSEXCRIS register is the raw interrupt status register. On a read, this register gives the current raw status value of the corresponding interrupt. A write has no effect.

System Exception Raw Interrupt Status (SYSEXCRIS)

Base 0x400F.9000 Offset 0x000 Type RO, reset 0x0000.0000



Bit/Field	Name	Туре	Reset	Description
31:6	reserved	RO	0x0000.00	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
5	FPIXCRIS	RO	0	Floating-Point Inexact Exception Raw Interrupt Status
				Value Description
				0 No interrupt
				1 A floating-point inexact exception has occurred.
				This bit is cleared by writing a 1 to the <code>IXCIC</code> bit in the SYSEXCIC register.
4	FPOFCRIS	RO	0	Floating-Point Overflow Exception Raw Interrupt Status
				Value Description
				0 No interrupt
				1 A floating-point overflow exception has occurred.
				This bit is cleared by writing a 1 to the OFCIC bit in the SYSEXCIC register.
3	FPUFCRIS	RO	0	Floating-Point Underflow Exception Raw Interrupt Status
				Value Description
				0 No interrupt
				A floating-point underflow exception has occurred.

This bit is cleared by writing a 1 to the UFCIC bit in the SYSEXCIC register.

Bit/Field	Name	Туре	Reset	Description
2	FPIOCRIS	RO	0	Floating-Point Invalid Operation Raw Interrupt Status
				Value Description 0 No interrupt 1 A floating-point invalid operation exception has occurred. This bit is cleared by writing a 1 to the IOCIC bit in the SYSEXCIC register.
1	FPDZCRIS	RO	0	Floating-Point Divide By 0 Exception Raw Interrupt Status Value Description 0 No interrupt 1 A floating-point divide by 0 exception has occurred.
0	FPIDCRIS	RO	0	This bit is cleared by writing a 1 to the DZCIC bit in the SYSEXCIC register. Floating-Point Input Denormal Exception Raw Interrupt Status Value Description 0 No interrupt 1 A floating-point input denormal exception has occurred.
				This bit is cleared by writing a 1 to the IDCIC bit in the SYSEXCIC

register.

Register 2: System Exception Interrupt Mask (SYSEXCIM), offset 0x004


The **SYSEXCIM** register is the interrupt mask set/clear register.

On a read, this register gives the current value of the mask on the relevant interrupt. Setting a bit allows the corresponding raw interrupt signal to be routed to the interrupt controller. Clearing a bit prevents the raw interrupt signal from being sent to the interrupt controller.

System Exception Interrupt Mask (SYSEXCIM)

Base 0x400F.9000 Offset 0x004

Type R/W, reset 0x0000.0000



Bit/Field	Name	Type	Reset	Description
31:6	reserved	R/W	0x0000.00	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
5	FPIXCIM	R/W	0	Floating-Point Inexact Exception Interrupt Mask
				Value Description
				O The FPIXCRIS interrupt is suppressed and not sent to the interrupt controller.
				An interrupt is sent to the interrupt controller when the FPISCRIS bit in the SYSEXCRIS register is set.
4	FPOFCIM	R/W	0	Floating-Point Overflow Exception Interrupt Mask
				Value Description
				O The FPOFCIS interrupt is suppressed and not sent to the interrupt controller.
				An interrupt is sent to the interrupt controller when the FPOFCRIS bit in the SYSEXCRIS register is set.
3	FPUFCIM	R/W	0	Floating-Point Underflow Exception Interrupt Mask
				Value Description
				O The FPUFCRIS interrupt is suppressed and not sent to the

1

interrupt controller.

An interrupt is sent to the interrupt controller when the ${\tt FPUFCRIS}$ bit in the ${\tt SYSEXCRIS}$ register is set.

Bit/Field	Name	Туре	Reset	Description
2	FPIOCIM	R/W	0	Floating-Point Invalid Operation Interrupt Mask
				Value Description
				O The FPIOCRIS interrupt is suppressed and not sent to the interrupt controller.
				An interrupt is sent to the interrupt controller when the FPIOCRIS bit in the SYSEXCRIS register is set.
1	FPDZCIM	R/W	0	Floating-Point Divide By 0 Exception Interrupt Mask
				Value Description
				O The FPDZCRIS interrupt is suppressed and not sent to the interrupt controller.
				An interrupt is sent to the interrupt controller when the FPDZCRIS bit in the SYSEXCRIS register is set.
0	FPIDCIM	R/W	0	Floating-Point Input Denormal Exception Interrupt Mask
				Value Description
				O The FPIDCRIS interrupt is suppressed and not sent to the interrupt controller.
				An interrupt is sent to the interrupt controller when the FPIDCRIS bit in the SYSEXCRIS register is set.

Register 3: System Exception Masked Interrupt Status (SYSEXCMIS), offset 0x008


The SYSEXCMIS register is the masked interrupt status register. On a read, this register gives the current masked status value of the corresponding interrupt. A write has no effect.

System Exception Masked Interrupt Status (SYSEXCMIS)

Base 0x400F.9000

Offset 0x008

Type RO, reset 0x0000.0000



register.

Bit/Field	Name	Туре	Reset	Description
2	FPIOCMIS	RO	0	Floating-Point Invalid Operation Masked Interrupt Status
				Value Description O An interrupt has not occurred or is masked. An unmasked interrupt was signaled due to an invalid operation. This bit is cleared by writing a 1 to the FPIOCIC bit in the SYSEXCIC register.
1	FPDZCMIS	RO	0	Floating-Point Divide By 0 Exception Masked Interrupt Status Value Description 0 An interrupt has not occurred or is masked. 1 An unmasked interrupt was signaled due to a divide by 0 exception.
				This bit is cleared by writing a 1 to the FPDZCIC bit in the SYSEXCIC register.
0	FPIDCMIS	RO	0	Floating-Point Input Denormal Exception Masked Interrupt Status Value Description
				An interrupt has not occurred or is masked.An unmasked interrupt was signaled due to an input denormal exception.
				This bit is cleared by writing a 1 to the FPIDCIC bit in the SYSEXCIC

register.

February 20, 2013 489


Register 4: System Exception Interrupt Clear (SYSEXCIC), offset 0x00C

The **SYSEXCIC** register is the interrupt clear register. On a write of 1, the corresponding interrupt (both raw interrupt and masked interrupt, if enabled) is cleared. A write of 0 has no effect.

System Exception Interrupt Clear (SYSEXCIC)

Base 0x400F.9000

Offset 0x00C Type W1C, reset 0x0000.0000



Bit/Field	Name	Type	Reset	Description
Divi icia	Name	Турс	Nosci	Description
31:6	reserved	W1C	0x0000.00	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
5	FPIXCIC	W1C	0	Floating-Point Inexact Exception Interrupt Clear
				Writing a 1 to this bit clears the FPIXCRIS bit in the SYSEXCRIS register and the FPIXCMIS bit in the SYSEXCMIS register.
4	FPOFCIC	W1C	0	Floating-Point Overflow Exception Interrupt Clear
				Writing a 1 to this bit clears the FPOFCRIS bit in the SYSEXCRIS register and the FPOFCMIS bit in the SYSEXCMIS register.
3	FPUFCIC	W1C	0	Floating-Point Underflow Exception Interrupt Clear
				Writing a 1 to this bit clears the FPUFCRIS bit in the SYSEXCRIS register and the FPUFCMIS bit in the SYSEXCMIS register.
2	FPIOCIC	W1C	0	Floating-Point Invalid Operation Interrupt Clear
				Writing a 1 to this bit clears the FPIOCRIS bit in the SYSEXCRIS register and the FPIOCMIS bit in the SYSEXCMIS register.
1	FPDZCIC	W1C	0	Floating-Point Divide By 0 Exception Interrupt Clear
				Writing a 1 to this bit clears the FPDZCRIS bit in the SYSEXCRIS register and the FPDZCMIS bit in the SYSEXCMIS register.
0	FPIDCIC	W1C	0	Floating-Point Input Denormal Exception Interrupt Clear Writing a 1 to this bit clears the FPIDCRIS bit in the SYSEXCRIS register and the FPIDCMIS bit in the SYSEXCMIS register.

7 Hibernation Module


The Hibernation Module manages removal and restoration of power to provide a means for reducing system power consumption. When the processor and peripherals are idle, power can be completely removed with only the Hibernation module remaining powered. Power can be restored based on an external signal or at a certain time using the built-in Real-Time Clock (RTC). The Hibernation module can be independently supplied from an external battery or an auxiliary power supply.

The Hibernation module has the following features:

- 32-bit real-time seconds counter (RTC) with 1/32,768 second resolution and a 15-bit sub-seconds counter
 - 32-bit RTC seconds match register and a 15-bit sub seconds match for timed wake-up and interrupt generation with 1/32,768 second resolution
 - RTC predivider trim for making fine adjustments to the clock rate
- Two mechanisms for power control
 - System power control using discrete external regulator
 - On-chip power control using internal switches under register control
- Dedicated pin for waking using an external signal
- RTC operational and hibernation memory valid as long as V_{DD} or V_{BAT} is valid
- Low-battery detection, signaling, and interrupt generation, with optional wake on low battery
- GPIO pin state can be retained during hibernation
- Clock source from a 32.768-kHz external crystal or oscillator
- Sixteen 32-bit words of battery-backed memory to save state during hibernation
- Programmable interrupts for:
 - RTC match
 - External wake
 - Low battery

7.1 Block Diagram

Figure 7-1. Hibernation Module Block Diagram



7.2 Signal Description

The following table lists the external signals of the Hibernation module and describes the function of each.

Table 7-1. Hibernate Signals (100LQFP)

Pin Name	Pin Number	Pin Mux / Pin Assignment	Pin Type	Buffer Type ^a	Description
GNDX	53	fixed	-	Power	GND for the Hibernation oscillator. When using a crystal clock source, this pin should only be connected to the crystal load capacitors to improve oscillator immunity to system noise. When using an external oscillator, this pin should be connected to GND.
HIB	51	fixed	0	TTL	An output that indicates the processor is in Hibernate mode.
VBAT	55	fixed	-	Power	Power source for the Hibernation module. It is normally connected to the positive terminal of a battery and serves as the battery backup/Hibernation module power-source supply.
WAKE	50	fixed	I	TTL	An external input that brings the processor out of Hibernate mode when asserted.

			_		
Pin Name	Pin Number	Pin Mux / Pin Assignment	Pin Type	Buffer Type ^a	Description
xosc0	52	fixed	I	Analog	Hibernation module oscillator crystal input or an external clock reference input. Note that this is either a 32.768-kHz crystal or a 32.768-kHz oscillator for the Hibernation module RTC.
XOSC1	54	fixed	0	Analog	Hibernation module oscillator crystal output. Leave unconnected when using a single-ended clock source.

Table 7-1. Hibernate Signals (100LQFP) (continued)

7.3 Functional Description

The Hibernation module provides two mechanisms for power control:

- The first mechanism uses internal switches to control power to the Cortex-M4F as well as to most analog and digital functions while retaining I/O pin power (VDD3ON mode).
- The second mechanism controls the power to the microcontroller with a control signal (HIB) that signals an external voltage regulator to turn on or off.

The Hibernation module power source is determined dynamically. The supply voltage of the Hibernation module is the larger of the main voltage source (V_{DD}) or the battery/auxilliary voltage source (V_{BAT}). The Hibernation module also has an independent clock source to maintain a real-time clock (RTC) when the system clock is powered down. Hibernate mode can be entered through one of two ways:

- The user initiates hibernation by setting the HIBREQ bit in the **Hibernation Control (HIBCTL)** register
- Power is arbitrarily removed from V_{DD} while a valid V_{BAT} is applied

Once in hibernation, the module signals an external voltage regulator to turn the power back on when an external pin ($\overline{\text{WAKE}}$) is asserted or when the internal RTC reaches a certain value. The Hibernation module can also detect when the battery voltage is low and optionally prevent hibernation or wake from hibernation when the battery voltage falls below a certain threshold.

When waking from hibernation, the $\overline{\mathtt{HIB}}$ signal is deasserted. The return of V_{DD} causes a POR to be executed. The time from when the $\overline{\mathtt{WAKE}}$ signal is asserted to when code begins execution is equal to the wake-up time (t_{WAKE} TO $_{HIB}$) plus the power-on reset time (t_{POR}).

7.3.1 Register Access Timing

Because the Hibernation module has an independent clocking domain, hibernation registers must be written only with a timing gap between accesses. The delay time is $t_{HIB_REG_ACCESS}$, therefore software must guarantee that this delay is inserted between back-to-back writes to Hibernation registers or between a write followed by a read. The wc interrupt in the **HIBMIS** register can be used to notify the application when the Hibernation modules registers can be accessed. Alternatively, software may make use of the wrc bit in the **Hibernation Control (HIBCTL)** register to ensure that the required timing gap has elapsed. This bit is cleared on a write operation and set once the write completes, indicating to software that another write or read may be started safely. Software should poll **HIBCTL** for wrc=1 prior to accessing any hibernation register.

a. The TTL designation indicates the pin has TTL-compatible voltage levels.


Back-to-back reads from Hibernation module registers have no timing restrictions. Reads are performed at the full peripheral clock rate.

7.3.2 Hibernation Clock Source

In systems where the Hibernation module is used, the module must be clocked by an external source that is independent from the main system clock, even if the RTC feature is not used. An external oscillator or crystal is used for this purpose. To use a crystal, a 32.768-kHz crystal is connected to the xosco and xosco pins. Alternatively, a 32.768-kHz oscillator can be connected to the xosco pin, leaving xosco unconnected. Care must be taken that the voltage amplitude of the 32.768-kHz oscillator is less than V_{BAT} , otherwise, the Hibernation module may draw power from the oscillator and not V_{BAT} during hibernation. See Figure 7-2 on page 494 and Figure 7-3 on page 495.

The Hibernation clock source is enabled by setting the CLK32EN bit of the **HIBCTL** register. The CLK32EN bit must be set before accessing any other Hibernation module register. If a crystal is used for the clock source, the software must leave a delay of t_{HIBOSC_START} after writing to the CLK32EN bit and before any other accesses to the Hibernation module registers. The delay allows the crystal to power up and stabilize. If an external oscillator is used for the clock source, no delay is needed. When using an external clock source, the OSCBYP bit in the **HIBCTL** register should be set. When using a crystal clock source, the GNDX pin should only be connected to the crystal load capacitors to improve oscillator immunity to system noise as shown in Figure 7-2 on page 494. When using an external clock source, the GNDX pin should be connected to GND.

Figure 7-2. Using a Crystal as the Hibernation Clock Source with a Single Battery Source



Note: X_1 = Crystal frequency is $f_{XOSC XTAL}$.

 $C_{1,2}$ = Capacitor value derived from crystal vendor load capacitance specifications.

 R_{PII} = Pull-up resistor is 200 k Ω

See "Hibernation Clock Source Specifications" on page 1392 for specific parameter values.




Figure 7-3. Using a Dedicated Oscillator as the Hibernation Clock Source with VDD3ON Mode 1

Note: R_{PU} = Pull-up resistor is 1 M Ω

7.3.3 System Implementation

Several different system configurations are possible when using the Hibernation module:

- Using a single battery source, where the battery provides both V_{DD} and V_{BAT}, as shown in Figure 7-2 on page 494.
- Using the VDD3ON mode, where V_{DD} continues to be powered in hibernation, allowing the GPIO pins to retain their states, as shown in Figure 7-3 on page 495. In this mode, V_{DDC} is powered off internally. The GPIO retention will be released when power is reapplied and the GPIOs will be initialized to their default values.
- Using separate sources for V_{DD} and V_{BAT}. In this mode, additional circuitry is required for system start-up without a battery or with a depleted battery, see the schematics for the EK-LM4F232 board for more information.
- Using a regulator to provide both V_{DD} and V_{BAT} with a switch enabled by HIB to remove V_{DD} during hibernation as shown in Figure 7-4 on page 496.

February 20, 2013 495

¹Some devices may not supply GNDX, WAKE or HIB signals.




Figure 7-4. Using a Regulator for Both V_{DD} and V_{BAT}

Adding external capacitance to the V_{BAT} supply reduces the accuracy of the low-battery measurement and should be avoided if possible. The diagrams referenced in this section only show the connection to the Hibernation pins and not to the full system.

If the application does not require the use of the Hibernation module, refer to "Connections for Unused Signals" on page 1374. In this situation, the HIB bit in the Run Mode Clock Gating Control Register 0 (RCGC0) and the Hibernation Run Mode Clock Gating Control (RCGCHIB) registers must be cleared, disabling the system clock to the Hibernation module and Hibernation module registers are not accessible.

7.3.4 Battery Management

Important: System-level factors may affect the accuracy of the low-battery detect circuit. The designer should consider battery type, discharge characteristics, and a test load during battery voltage measurements.

The Hibernation module can be independently powered by a battery or an auxiliary power source using the \mathtt{VBAT} pin. The module can monitor the voltage level of the battery and detect when the voltage drops below $\mathsf{V}_{\mathtt{LOWBAT}}$. The voltage threshold can be between 1.9 V and 2.5 V and is configured using the $\mathtt{VBATSEL}$ field in the **HIBCTL** register. The module can also be configured so that it does not go into Hibernate mode if the battery voltage drops below this threshold. In addition, battery voltage is monitored while in hibernation, and the microcontroller can be configured to wake from hibernation if the battery voltage goes below the threshold using the BATWKEN bit in the **HIBCTL** register.

The Hibernation module is designed to detect a low-battery condition and set the LOWBAT bit of the **Hibernation Raw Interrupt Status (HIBRIS)** register when this occurs. If the VABORT bit in the **HIBCTL** register is also set, then the module is prevented from entering Hibernate mode when a low-battery is detected. The module can also be configured to generate an interrupt for the low-battery condition (see "Interrupts and Status" on page 500).

Note that the Hibernation module draws power from whichever source (V_{BAT} or V_{DD}) has the higher voltage. Therefore, it is important to design the circuit to ensure that V_{DD} is higher than V_{BAT} under nominal conditions or else the Hibernation module draws power from the battery even when V_{DD} is available.

7.3.5 Real-Time Clock

The RTC module is designed to keep wall time. The RTC can operate in seconds counter mode or calendar mode. A 32.768 kHz clock source along with a 15-bit pre-divider reduces the clock to 1 Hz. The 1 Hz clock is used to increment the 32-bit counter and keep track of seconds. A match register can be configured to interrupt or wake the system from hibernate. In addition, a software trim register is implemented to allow the user to compensate for oscillator inaccuracies using software.

7.3.5.1 RTC Counter - Seconds/Subseconds Mode

The clock signal to the RTC is provided by either of the 32.768-kHz clock sources available to the Hibernation module. The **Hibernation RTC Counter (HIBRTCC)** register displays the seconds value. The **Hibernation RTC Sub Seconds register (HIBRTCSS)** is provided for additional time resolution of an application requiring less than one-second divisions.

The RTC is enabled by setting the RTCEN bit of the **HIBCTL** register. The RTC counter and sub-seconds counters begin counting immediately once RTCEN is set. Both counters count up. The RTC continues counting as long as the RTC is enabled and a valid V_{BAT} is present, regardless of whether V_{DD} is present or if the device is in hibernation.

The HIBRTCC register is set by writing the Hibernation RTC Load (HIBRTCLD) register. A write to the HIBRTCLD register clears the 15-bit sub-seconds counter field, RTCSSC, in the HIBRTCSS register. To ensure a valid read of the RTC value, the HIBRTCC register should be read first, followed by a read of the RTCSSC field in the HIBRTCSS register and then a re-read of the HIBRTCC register. If the two values for the HIBRTCC are equal, the read is valid. By following this procedure, errors in the application caused by the HIBRTCC register rolling over by a count of 1 during a read of the RTCSSC field are prevented. The RTC can be configured to generate an alarm by setting the RTCAL0 bit in the HIBIM register. When an RTC match occurs, an interrupt is generated and displayed in the HIBRIS register. Refer to "RTC Match - Seconds/Subseconds Mode" on page 497 for more information.

If the RTC is enabled, only a cold POR, where both V_{BAT} and V_{DD} are removed, resets the RTC registers. If any other reset occurs while the RTC is enabled, such as an external \overline{RST} assertion or BOR reset, the RTC is not reset. If the RTC is not enabled, the RTC registers can be reset under any type of system reset as long as the external wake pins are not enabled.

7.3.5.2 RTC Match - Seconds/Subseconds Mode

The Hibernation module includes a 32-bit match register, **HIBRTCM0**, which is compared to the value of the RTC 32-bit counter, **HIBRTCC**. The match functionality also extends to the sub-seconds counter. The 15-bit field (RTCSSM) in the **HIBRTCSS** register is compared to the value of the 15-bit sub-seconds counter. When a match occurs, the RTCALT0 bit is set in the **HIBRIS** register. For applications using Hibernate mode, the processor can be programmed to wake from Hibernate mode by setting the RTCWEN bit in the **HIBCTL** register. The processor can also be programmed to generate an interrupt to the interrupt controller by setting the RTCALT0 bit in the **HIBIM** register.

The match interrupt generation takes priority over an interrupt clear. Therefore, writes to the RTCALTO bit in the **Hibernation Interrupt Clear (HIBIC)** register do not clear the RTCALTO bit if the **HIBRTCC** value and the **HIBRTCMO** value are equal. There are several methodologies to avoid this occurrence, such as writing a new value to the **HIBRTCLD** register prior to writing the **HIBIC** to clear the RTCALTO. Another example, would be to disable the RTC and re-enable the RTC by clearing and setting the RTCEN bit in the **HIBCTL** register.

Note: A Hibernate request made while a match event is valid causes the module to immediately wake up. This occurs when the RTCWEN bit is set and the RTCALTO bit in the HIBRIS register is set at the same time the HIBREQ bit in the HIBCTL register is written to a 1. This can be

avoided by clearing the RTCAL0 bit in the **HIBRIS** register by writing a 1 to the corresponding bit in the **HIBIC** register before setting the HIBREQ bit. Another example would be to disable the RTC and re-enable the RTC by clearing and setting the RTCEN bit in the **HIBCTL** register.

7.3.5.3 RTC Trim

The RTC counting rate can be adjusted to compensate for inaccuracies in the clock source by using the predivider trim register, **HIBRTCT**. This register has a nominal value of 0x7FFF, and is used for one second out of every 64 seconds in RTC counter mode, when bits [5:0] in the **HIBRTCC** register change from 0x00 to 0x01, to divide the input clock. This configuration allows the software to make fine corrections to the clock rate by adjusting the predivider trim register up or down from 0x7FFF. The predivider trim should be adjusted up from 0x7FFF in order to slow down the RTC rate and down from 0x7FFF in order to speed up the RTC rate.

Care must be taken when using trim values that are near to the sub seconds match value in the **HIBRTCSS** register. It is possible when using trim values above 0x7FFF to receive two match interrupts for the same counter value. In addition, it is possible when using trim values below 0x7FFF to miss a match interrupt.

In the case of a trim value above 0x7FFF, when the RTCSSC value in the **HIBRTCSS** register reaches 0x7FFF, the RTCC value increments from 0x0 to 0x1 while the RTCSSC value is decreased by the trim amount. The RTCSSC value is counted up again to 0x7FFF before rolling over to 0x0 to begin counting up again. If the match value is within this range, the match interrupt is triggered twice. For example, as shown in Table 7-2 on page 498, if the match interrupt was configured with RTCM0=0x1 and RTCSSM=0x7FFD, two interrupts would be triggered.

Table 7-2. Counter Behavior with a TRIM Value of 0x8003

RTCC [6:0]	RTCSSC
0x00	0x7FFD
0x00	0x7FFE
0x00	0x7FFF
0x01	0x7FFC
0x01	0x7FFD
0x01	0x7FFE
0x01	0x7FFF
0x01	0x0
0x01	0x1
-	-
0x01	0x7FFB
0x01	0x7FFC
0x01	0x7FFD
0x01	0x7FFE
0x01	0x7FFF
0x02	0x0

In the case of a trim value below 0x7FFF, the RTCSSC value is advanced from 0x7FFF to the trim value while the RTCC value is incremented from 0x0 to 0x1. If the match value is within that range, the match interrupt is not triggered. For example, as shown in Table 7-3 on page 499, if the match interrupt was configured with RTCM0=0x1 and RTCSSM=0x2,an interrupt would never be triggered.

Table 7-3. Counter Behavior with a TRIM Value of 0x7FFC

RTCC [6:0]	RTCSSC
0x00	0x7FFD
0x00	0x7FFE
0x00	0x7FFF
0x01	0x3
0x01	0x4
0x01	0x5

7.3.6 Battery-Backed Memory

The Hibernation module contains 16 32-bit words of memory that are powered from the battery or an auxiliary power supply and therefore retained during hibernation. The processor software can save state information in this memory prior to hibernation and recover the state upon waking. The battery-backed memory can be accessed through the **HIBDATA** registers. If both V_{DD} and V_{BAT} are removed, the contents of the **HIBDATA** registers are not retained.

7.3.7 Power Control Using HIB

Important: The Hibernation Module requires special system implementation considerations when using HIB to control power, as it is intended to power-down all other sections of the microcontroller. All system signals and power supplies that connect to the chip must be driven to 0 V or powered down with the same regulator controlled by HIB.

The Hibernation module controls power to the microcontroller through the use of the $\overline{\text{HIB}}$ pin which is intended to be connected to the enable signal of the external regulator(s) providing 3.3 V to the microcontroller and other circuits. When the $\overline{\text{HIB}}$ signal is asserted by the Hibernation module, the external regulator is turned off and no longer powers the microcontroller and any parts of the system that are powered by the regulator. The Hibernation module remains powered from the V_{BAT} supply (which could be a battery or an auxiliary power source) until a Wake event. Power to the microcontroller is restored by deasserting the $\overline{\text{HIB}}$ signal, which causes the external regulator to turn power back on to the chip.

7.3.8 Power Control Using VDD3ON Mode

The Hibernation module may also be configured to cut power to all internal modules during Hibernate mode. While in this state, if VDD3ON is set in the **HIBCTL** register, all pins are held in the state they were in prior to entering hibernation. For example, inputs remain inputs; outputs driven high remain driven high, and so on.

In the VDD3ON mode, the regulator should maintain 3.3 V power to the microcontroller during Hibernate. GPIO retention is disabled when the RETCLR bit is cleared in the **HIBCTL** register.

7.3.9 Initiating Hibernate

Hibernate mode is initiated when the <code>HIBREQ</code> bit of the <code>HIBCTL</code> register is set. If a wake-up condition has not been configured using the <code>PINWEN</code> or <code>RTCWEN</code> bits in the <code>HIBCTL</code> register, the hibernation request is ignored. If a Flash memory write operation is in progress when the <code>HIBREQ</code> bit is set, an interlock feature holds off the transition into Hibernate mode until the write has completed. In addition, if the battery voltage is below the threshold voltage defined by the <code>VBATSEL</code> field in the <code>HIBCTL</code> register, the hibernation request is ignored.

7.3.10 Waking from Hibernate

The Hibernation module is configured to wake from the external WAKE pin by setting the PINWEN bit of the **HIBCTL** register. It is configured to wake from RTC match by setting the RTCWEN bit. Note that the WAKE pin uses the Hibernation module's internal power supply as the logic 1 reference.

The Hibernation module can also be configured to wake from hibernate when the following events occur:

- RTC match wake event
- Low Battery wake event

By setting the RTCWEN bit in the **HIBCTL** register a wake from hibernate can occur when the value of the **HIBRTCC** register matches the value of the **HIBRTCM0** register and the value of the RTCSSC field matches the RTCSSM field in the **HIBRTCSS** register.

To allow a wake from Hibernate on a low battery event, the BATWKEN bit in the **HIBCTL** register must be set. In this configuration, the battery voltage is checked every 512 seconds while in hibernation. If the voltage is below the level specified by the VBATSEL field, the LOWBAT interrupt is set in the **HIBRIS** register.

Upon external wake-up, external reset, or RTC match, the Hibernation module delays coming out of hibernation until V_{DD} is above the minimum specified voltage, see Table 24-5 on page 1378.

When the Hibernation module wakes, the microcontroller performs a normal power-on reset. Note that this reset does not reset the Hibernation module, but does reset the rest of the microcontroller. Software can detect that the power-on was due to a wake from hibernation by examining the raw interrupt status register (see "Interrupts and Status" on page 500) and by looking for state data in the battery-backed memory (see "Battery-Backed Memory" on page 499).

7.3.11 Arbitrary Power Removal

If the CLK32EN bit is set and either the PINWEN bit or the RTCEN bit is set, the microcontroller goes into hibernation if V_{DD} is arbitrarily removed. The microcontroller wakes from hibernation when power is reapplied. If the CLK32EN bit is set but neither the PINWEN bit nor the RTCEN bit is set, the microcontroller still goes into hibernation if power is removed, however, when V_{DD} is reapplied, the MCU executes a cold POR and the Hibernation module is reset. If the CLK32EN bit is not set and V_{DD} is arbitrarily removed, the part is simply powered off and executes a cold POR when power is reapplied.

If V_{DD} is arbitrarily removed while a Flash memory write operation is in progress, the write operation must be retried after V_{DD} is reapplied.

7.3.12 Interrupts and Status

The Hibernation module can generate interrupts when the following conditions occur:

- Assertion of WAKE pin
- RTC match
- Low battery detected
- Write complete/capable

All of the interrupts are ORed together before being sent to the interrupt controller, so the Hibernate module can only generate a single interrupt request to the controller at any given time. The software interrupt handler can service multiple interrupt events by reading the **Hibernation Masked Interrupt Status (HIBMIS)** register. Software can also read the status of the Hibernation module at any time by reading the **HIBRIS** register which shows all of the pending events. This register can be used after waking from hibernation to see if a wake condition was caused by one of the events above or by a power loss.

The events that can trigger an interrupt are configured by setting the appropriate bits in the **Hibernation Interrupt Mask (HIBIM)** register. Pending interrupts can be cleared by writing the corresponding bit in the **Hibernation Interrupt Clear (HIBIC)** register.

7.4 Initialization and Configuration

The Hibernation module has several different configurations. The following sections show the recommended programming sequence for various scenarios. Because the Hibernation module runs at a low frequency and is asynchronous to the rest of the microcontroller, which is run off the system clock, software must allow a delay of $t_{\text{HIB_REG_ACCESS}}$ after writes to registers (see "Register Access Timing" on page 493). The WC interrupt in the **HIBMIS** register can be used to notify the application when the Hibernation modules registers can be accessed.

7.4.1 Initialization

The Hibernation module comes out of reset with the system clock enabled to the module, but if the system clock to the module has been disabled, then it must be re-enabled, even if the RTC feature is not used. See page 334.

If a 32.768-kHz crystal is used as the Hibernation module clock source, perform the following steps:

- 1. Write 0x0000.0010 to the **HIBIM** register to enable the WC interrupt.
- 2. Write 0x40 to the **HIBCTL** register at offset 0x10 to enable the oscillator input.
- **3.** Wait until the WC interrupt in the **HIBMIS** register has been triggered before performing any other operations with the Hibernation module.

If a 32.768-kHz single-ended oscillator is used as the Hibernation module clock source, then perform the following steps:

- 1. Write 0x0000.0010 to the **HIBIM** register to enable the wc interrupt.
- 2. Write 0x0001.0040 to the **HIBCTL** register at offset 0x10 to enable the oscillator input and bypass the on-chip oscillator.
- 3. Wait until the wc interrupt in the **HIBMIS** register has been triggered before performing any other operations with the Hibernation module.

The above steps are only necessary when the entire system is initialized for the first time. If the microcontroller has been in hibernation, then the Hibernation module has already been powered up and the above steps are not necessary. The software can detect that the Hibernation module and clock are already powered by examining the CLK32EN bit of the **HIBCTL** register.

Table 7-4 on page 502 illustrates how the clocks function with various bit setting both in normal operation and in hibernation.

Table 7-4. Hibernation Module Clock Operation

CLK32EN	PINWEN	RTCWEN	RTCEN	Result Normal Operation	Result Hibernation
0	Х	Х	Х	Hibernation module disabled	Hibernation module disabled
1	0	0	1	RTC match capability enabled.	No hibernation
1	0	1	1	Module clocked	RTC match for wake-up event
1	1	0	0	Module clocked	Clock is powered down during hibernation and powered up again on external wake-up event.
1	1	0	1	Module clocked	Clock is powered up during hibernation for RTC. Wake up on external event.
1	1	1	1	Module clocked	RTC match or external wake-up event, whichever occurs first.

7.4.2 RTC Match Functionality (No Hibernation)

Use the following steps to implement the RTC match functionality of the Hibernation module:

- Write 0x0000.0040 to the HIBCTL register at offset 0x010 to enable 32.768-kHz Hibernation oscillator.
- 2. Write the required RTC match value to the **HIBRTCM0** register at offset 0x004 and the RTCSSM field in the **HIBRTCSS** register at offset 0x028.
- **3.** Write the required RTC load value to the **HIBRTCLD** register at offset 0x00C.
- 4. Set the required RTC match interrupt mask in the RTCALT0 in the HIBIM register at offset 0x014.
- 5. Write 0x0000.0041 to the **HIBCTL** register at offset 0x010 to enable the RTC to begin counting.

7.4.3 RTC Match/Wake-Up from Hibernation

Use the following steps to implement the RTC match and wake-up functionality of the Hibernation module:

- 1. Write 0x0000.0040 to the **HIBCTL** register at offset 0x010 to enable 32.768-kHz Hibernation oscillator.
- 2. Write the required RTC match value to the **HIBRTCM0** register at offset 0x004 and the RTCSSM field in the **HIBRTCSS** register at offset 0x028.
- **3.** Write the required RTC load value to the **HIBRTCLD** register at offset 0x00C. This write causes the 15-bit sub seconds counter to be cleared.
- 4. Write any data to be retained during power cut to the HIBDATA register at offsets 0x030-0x06F.
- 5. Set the RTC Match Wake-Up and start the hibernation sequence by writing 0x0000.004B to the **HIBCTL** register at offset 0x010.

7.4.4 External Wake-Up from Hibernation

Use the following steps to implement the Hibernation module with the external \overline{WAKE} pin as the wake-up source for the microcontroller:

1. Write 0x0000.0040 to the **HIBCTL** register at offset 0x010 to enable 32.768-kHz Hibernation oscillator.

- 2. Write any data to be retained during power cut to the **HIBDATA** register at offsets 0x030-0x06F.
- **3.** Enable the external wake and start the hibernation sequence by writing 0x0000.0052 to the **HIBCTL** register at offset 0x010.

7.4.5 RTC or External Wake-Up from Hibernation

- Write 0x0000.0040 to the HIBCTL register at offset 0x010 to enable 32.768-kHz Hibernation oscillator.
- 2. Write the required RTC match value to the **HIBRTCM0** register at offset 0x004 and the RTCSSM field in the **HIBRTCSS** register at offset 0x028.
- **3.** Write the required RTC load value to the **HIBRTCLD** register at offset 0x00C. This write causes the 15-bit sub seconds counter to be cleared.
- **4.** Write any data to be retained during power cut to the **HIBDATA** register at offsets 0x030-0x06F.
- **5.** Set the RTC Match/External Wake-Up and start the hibernation sequence by writing 0x0000.005B to the **HIBCTL** register at offset 0x010.

7.5 Register Map

Table 7-5 on page 503 lists the Hibernation registers. All addresses given are relative to the Hibernation Module base address at 0x400F.C000. Note that the system clock to the Hibernation module must be enabled before the registers can be programmed (see page 334). There must be a delay of 3 system clocks after the Hibernation module clock is enabled before any Hibernation module registers are accessed. In addition, the CLK32EN bit in the **HIBCTL** register must be set before accessing any other Hibernation module register.

Note: The Hibernation module registers are on the Hibernation module clock domain and have special timing requirements. Software should make use of the WRC bit in the **HIBCTL** register to ensure that the required timing gap has elapsed. If the WRC bit is clear, any attempted write access is ignored. See "Register Access Timing" on page 493.

Important: The Hibernation module registers are reset under two conditions:

- 1. Any type of system reset (if the RTCEN and the PINWEN bits in the **HIBCTL** register are clear).
- **2.** A cold POR occurs when both the V_{DD} and V_{BAT} supplies are removed.

Any other reset condition is ignored by the Hibernation module.

Table 7-5. Hibernation Module Register Map

Offset	Name	Туре	Reset	Description	See page
0x000	HIBRTCC	RO	0x0000.0000	Hibernation RTC Counter	505
0x004	HIBRTCM0	R/W	0xFFFF.FFFF	Hibernation RTC Match 0	506
0x00C	HIBRTCLD	R/W	0x0000.0000	Hibernation RTC Load	507
0x010	HIBCTL	R/W	0x8000.2000	Hibernation Control	508

Table 7-5. Hibernation Module Register Map (continued)

Offset	Name	Туре	Reset	Description	See page
0x014	HIBIM	R/W	0x0000.0000	Hibernation Interrupt Mask	512
0x018	HIBRIS	RO	0x0000.0000	Hibernation Raw Interrupt Status	514
0x01C	HIBMIS	RO	0x0000.0000	Hibernation Masked Interrupt Status	516
0x020	HIBIC	R/W1C	0x0000.0000	Hibernation Interrupt Clear	518
0x024	HIBRTCT	R/W	0x0000.7FFF	Hibernation RTC Trim	519
0x028	HIBRTCSS	R/W	0x0000.0000	Hibernation RTC Sub Seconds	520
0x030- 0x06F	HIBDATA	R/W	-	Hibernation Data	521

7.6 Register Descriptions

The remainder of this section lists and describes the Hibernation module registers, in numerical order by address offset.

Register 1: Hibernation RTC Counter (HIBRTCC), offset 0x000

This register is the current 32-bit value of the RTC counter.


The RTC counter consists of a 32-bit seconds counter and a 15-bit sub seconds counter. The RTC counters are reset by the Hibernation module reset. The RTC 32-bit seconds counter can be set by the user using the **HIBRTCLD** register. When the 32-bit seconds counter is set, the 15-bit sub second counter is cleared.

The RTC value can be read by first reading the **HIBRTCC** register, reading the RTCSSC field in the **HIBRTCS** register, and then rereading the **HIBRTCC** register. If the two values for **HIBRTCC** are equal, the read is valid.

Hibernation RTC Counter (HIBRTCC)

Base 0x400F.C000 Offset 0x000

Type RO, reset 0x0000.0000



A read returns the 32-bit counter value, which represents the seconds elapsed since the RTC was enabled. This register is read-only. To change the value, use the **HIBRTCLD** register.

Register 2: Hibernation RTC Match 0 (HIBRTCM0), offset 0x004


This register is the 32-bit seconds match register for the RTC counter. The 15-bit sub second match value is stored in the reading the RTCSSC field in the **HIBRTCSS** register and can be used in conjunction with this register for a more precise time match.

Note: The Hibernation module registers are on the Hibernation module clock domain and have special timing requirements. Software should make use of the WRC bit in the HIBCTL register to ensure that the required timing gap has elapsed. If the WRC bit is clear, any attempted write access is ignored. See "Register Access Timing" on page 493.

Hibernation RTC Match 0 (HIBRTCM0)

Base 0x400F.C000 Offset 0x004

Type R/W, reset 0xFFFF.FFF



Bit/Field Name Type Reset Description

31:0 RTCM0 R/W 0xFFF.FFFF RTC Match 0

A write loads the value into the RTC match register.

A read returns the current match value.

Register 3: Hibernation RTC Load (HIBRTCLD), offset 0x00C


This register is used to load a 32-bit value loaded into the RTC counter. The load occurs immediately upon this register being written. When this register is written, the 15-bit sub seconds counter is also cleared.

Note: The Hibernation module registers are on the Hibernation module clock domain and have special timing requirements. Software should make use of the WRC bit in the **HIBCTL** register to ensure that the required timing gap has elapsed. If the WRC bit is clear, any attempted write access is ignored. See "Register Access Timing" on page 493.

Hibernation RTC Load (HIBRTCLD)

Base 0x400F.C000

Offset 0x00C Type R/W, reset 0x0000.0000



A write loads the current value into the RTC counter (RTCC).

A read returns the 32-bit load value.

Register 4: Hibernation Control (HIBCTL), offset 0x010

This register is the control register for the Hibernation module. This register must be written last before a hibernate event is issued. Writes to other registers after the HIBREQ bit is set are not guaranteed to complete before hibernation is entered.


Note: Writes to this register have special timing requirements. Software should make use of the WRC bit in the HIBCTL register to ensure that the required synchronization has elapsed. While the WRC bit is clear, any attempts to write this register are ignored. Reads may occur at any time.

Hibernation Control (HIBCTL)

Base 0x400F.C000 Offset 0x010

Dit/Eiold

Type R/W, reset 0x8000.2000



DIVI ICIU	INAIIIE	Type	Neset	Description
31	WRC	RO	1	Write Complete/Capable

Value Description

- The interface is processing a prior write and is busy. Any write operation that is attempted while WRC is 0 results in undetermined behavior.
- 1 The interface is ready to accept a write.

Software must poll this bit between write requests and defer writes until WRC=1 to ensure proper operation. An interrupt can be configured to indicate the WRC has completed.

The bit name WRC means "Write Complete," which is the normal use of the bit (between write accesses). However, because the bit is set out-of-reset, the name can also mean "Write Capable" which simply indicates that the interface may be written to by software. This difference may be exploited by software at reset time to detect which method of programming is appropriate: 0 = software delay loops required; 1 = WRC paced available.

30:18 reserved RO 0x000

Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.

Bit/Field	Name	Туре	Reset	Description
17	OSCDRV	R/W	0	Oscillator Drive Capability
				This bit is used to compensate for larger or smaller filtering capacitors.
				Note: This bit is not meant to be changed once the Hibernation oscillator has started. Oscillator stability is not guaranteed if the user changes this value after the the oscillator is running.
				Value Description
				0 Low drive strength is enabled, 12 pF.
				1 High drive strength is enabled, 24 pF.
16	OSCBYP	R/W	0	Oscillator Bypass
				Value Description
				The internal 32.768-kHz Hibernation oscillator is enabled. This bit should be cleared when using an external 32.768-kHz crystal.
				The internal 32.768-kHz Hibernation oscillator is disabled and powered down. This bit should be set when using a single-ended oscillator attached to XOSCO.
15	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
14:13	VBATSEL	R/W	0x1	Select for Low-Battery Comparator
				This field selects the battery level that is used when checking the battery status. If the battery voltage is below the specified level, the LOWBAT interrupt bit in the HIBRIS register is set.
				Value Description
				0x0 1.9 Volts
				0x1 2.1 Volts (default)
				0x2 2.3 Volts
				0x3 2.5 Volts
12:11	reserved	RO	0x0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
10	BATCHK	R/W	0	Check Battery Status
				Value Description
				When read, indicates that the low-battery comparator cycle is not active.
				Writing a 0 has no effect.
				When read, indicates the low-battery comparator cycle has not completed.
				Setting this bit initiates a low-battery comparator cycle. If the battery voltage is below the level specified by VBATSEL field, the LOWBAT interrupt bit in the HIBRIS register is set. A hibernation request is held off if a battery check is in progress.

Bit/Field	Name	Туре	Reset	Description
9	BATWKEN	R/W	0	Wake on Low Battery
				Value Description
				The battery voltage level is not automatically checked. Low battery voltage does not cause the microcontroller to wake from hibernation.
				When this bit is set, the battery voltage level is checked every 512 seconds while in hibernation. If the voltage is below the level specified by VBATSEL field, the microcontroller wakes from hibernation and the LOWBAT interrupt bit in the HIBRIS register is set.
8	VDD3ON	R/W	0	VDD Powered
				Value Description
				The internal switches are not used. The HIB signal should be used to control an external switch or regulator.
				The internal switches control the power to the on-chip modules (VDD3ON mode).
				Regardless of the status of the VDD30N bit, the $\overline{\tt HIB}$ signal is asserted during Hibernate mode. Thus, when VDD30N is set, the $\overline{\tt HIB}$ signal should not be connected to the 3.3V regulator, and the 3.3V power source should remain connected. When this bit is set while in hibernation, all pins are held in the state they were in prior to entering hibernation. For example, inputs remain inputs; outputs driven high remain driven high, and so on.
7	VABORT	R/W	0	Power Cut Abort Enable
				Value Description
				The microcontroller goes into hibernation regardless of the voltage level of the battery.
				When this bit is set, the battery voltage level is checked before entering hibernation. If V _{BAT} is less than the voltage specified by VBATSEL, the microcontroller does not go into hibernation.
6	CLK32EN	R/W	0	Clocking Enable
				This bit must be enabled to use the Hibernation module.
				Value Description
				The Hibernation module clock source is disabled.
				1 The Hibernation module clock source is enabled.
5	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.

Bit/Field	Name	Туре	Reset	Description	n
4	PINWEN	R/W	0	External W	/ake Pin Enable
				Value	Description
				0	The status of the $\overline{\mathtt{WAKE}}$ pin has no effect on hibernation.
				1	An assertion of the $\overline{\mathtt{WAKE}}$ pin takes the microcontroller out of hibernation.
3	RTCWEN	R/W	0	RTC Wake	e-up Enable
				Value	Description
				0	An RTC match event has no effect on hibernation.
					An RTC match event (the value the HIBRTCC register matches the value of the HIBRTCM0 register and the value of the RTCSSC field matches the RTCSSM field in the HIBRTCSS register) takes the microcontroller out of hibernation.
2	reserved	RO	0	compatibil	should not rely on the value of a reserved bit. To provide ity with future products, the value of a reserved bit should be across a read-modify-write operation.
1	HIBREQ	R/W	0	Hibernatio	n Request
				Value	Description
				0	No hibernation request.
				1	Set this bit to initiate hibernation.
				After a wa	ke-up event, this bit is automatically cleared by hardware.
					ion request is ignored if both the PINWEN and RTCWEN bits
				A hibernat	ion request is held off if the BATCHK bit is set.
0	RTCEN	R/W	0	RTC Time	r Enable
				Value	Description
				0	The Hibernation module RTC is disabled.
				1	The Hibernation module RTC is enabled.

February 20, 2013 511

Register 5: Hibernation Interrupt Mask (HIBIM), offset 0x014


This register is the interrupt mask register for the Hibernation module interrupt sources. Each bit in this register masks the corresponding bit in the **Hibernation Raw Interrupt Status (HIBRIS)** register. If a bit is unmasked, the interrupt is sent to the interrupt controller. If the bit is masked, the interrupt is not sent to the interrupt controller. The WC bit of the **HIBIM** register may be set before the CLK32EN bit of the **HIBCTL** register is set. This allows software to use the WC interrupt trigger to detect when the RTCOSC clock is stable, which may be in excess of one second. If the WC bit is set before the CLK32EN has been set, the mask value is not preserved over a hibernate cycle unless the bit is written a second time.

Note: The WC bit of this register is in the system clock domain such that a write to this bit is immediate and may be done before the CLK32EN bit is set in the **HIBCTL** register.

Hibernation Interrupt Mask (HIBIM)

Base 0x400F.C000 Offset 0x014

Type R/W, reset 0x0000.0000



Bit/Field	Name	Type	Reset	Description
31:5	reserved	RO	0x0000.000	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
4	WC	R/W	0	External Write Complete/Capable Interrupt Mask
				Value Description
				The WC interrupt is suppressed and not sent to the interrupt controller.
				1 An interrupt is sent to the interrupt controller when the wc bit in the HIBRIS register is set.
3	EXTW	R/W	0	External Wake-Up Interrupt Mask

Value Description

- The EXTW interrupt is suppressed and not sent to the interrupt controller.
- 1 An interrupt is sent to the interrupt controller when the EXTW bit in the HIBRIS register is set.

Bit/Field	Name	Туре	Reset	Description
2	LOWBAT	R/W	0	Low Battery Voltage Interrupt Mask
				Value Description
				O The LOWBAT interrupt is suppressed and not sent to the interrupt controller.
				An interrupt is sent to the interrupt controller when the LOWBAT bit in the HIBRIS register is set.
1	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
0	RTCALT0	R/W	0	RTC Alert 0 Interrupt Mask
				Value Description
				0 The RTCALTO interrupt is suppressed and not sent to the interrupt controller.
				An interrupt is sent to the interrupt controller when the RTCALTO bit in the HIBRIS register is set.

Register 6: Hibernation Raw Interrupt Status (HIBRIS), offset 0x018

This register is the raw interrupt status for the Hibernation module interrupt sources. Each bit can be masked by clearing the corresponding bit in the **HIBIM** register. When a bit is masked, the interrupt is not sent to the interrupt controller. Bits in this register are cleared by writing a 1 to the corresponding bit in the **Hibernation Interrupt Clear (HIBIC)** register or by entering hibernation.

Note: The bits in this register do not reflect hibernation due to an arbitrary power loss on V_{DD}. If the LOWBAT bit was set prior to the loss of power, it will still be set when power is reapplied. In addition, the EXTW bit is self-clearing when exiting from hibernation, so if it was set prior to the power loss, the event is lost after the power is reapplied.

Hibernation Raw Interrupt Status (HIBRIS)

Base 0x400F.C000 Offset 0x018 Type RO, reset 0x0000.0000

	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16
		1			 			rese	rved					1		
Type	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO
Reset	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0
	15	14	13	12	11	10	9	8	7	6	5	4	3	2	1	0
		1			 	reserved		'				WC	EXTW	LOWBAT	reserved	RTCALT0
Type	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO
Reset	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0

Bit/Field	Name	Туре	Reset	Description
31:5	reserved	RO	0x0000.000	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
4	WC	RO	0	Write Complete/Capable Raw Interrupt Status
				Value Description
				The wrc bit in the HIBCTL has not been set.
				1 The WRC bit in the HIBCTL has been set.
				This bit is cleared by writing a 1 to the wc bit in the HIBIC register.
3	EXTW	RO	0	External Wake-Up Raw Interrupt Status
				Note that the $\overline{\mathtt{WAKE}}$ signal is cleared after the interrupt is registered in the Hibernation module.
				Value Description
				The WAKE pin has not been asserted.
				1 The WAKE pin has been asserted.
				This bit is cleared by writing a 1 to the EXTW bit in the HIBIC register.
2	LOWBAT	RO	0	Low Battery Voltage Raw Interrupt Status
				Value Description
				The battery voltage has not dropped below V _{LOWBAT} .
				1 The battery voltage dropped below V _{LOWBAT} .

This bit is cleared by writing a 1 to the LOWBAT bit in the **HIBIC** register.

Bit/Field	Name	Туре	Reset	Description
1	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
0	RTCALT0	RO	0	RTC Alert 0 Raw Interrupt Status
				Value Description
				0 No match
				The value of the HIBRTCC register matches the value in the HIBRTCM0 register and the value of the RTCSSC field matches the RTCSSM field in the HIBRTCSS register.

This bit is cleared by writing a 1 to the ${\tt RTCALT0}$ bit in the HIBIC register.


Register 7: Hibernation Masked Interrupt Status (HIBMIS), offset 0x01C

This register is the masked interrupt status for the Hibernation module interrupt sources. Bits in this register are the AND of the corresponding bits in the HIBRIS and HIBIM registers. When both corresponding bits are set, the bit in this register is set, and the interrupt is sent to the interrupt controller.

Hibernation Masked Interrupt Status (HIBMIS)

Base 0x400F.C000

Offset 0x01C Type RO, reset 0x0000.0000



Bit/Field	Name	Type	Reset	Description
31:5	reserved	RO	0x0000.000	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
4	WC	RO	0	Write Complete/Capable Masked Interrupt Status
				Value Description
				The WRC bit has not been set or the interrupt is masked.
				An unmasked interrupt was signaled due to the WRC bit being set.
				This bit is cleared by writing a 1 to the \mathtt{WC} bit in the HIBIC register.
3	EXTW	RO	0	External Wake-Up Masked Interrupt Status
				Value Description
				O An external wake-up interrupt has not occurred or is masked.
				An unmasked interrupt was signaled due to a $\overline{\mathtt{WAKE}}$ pin assertion.
				This bit is cleared by writing a 1 to the EXTW bit in the HIBIC register.
2	LOWBAT	RO	0	Low Battery Voltage Masked Interrupt Status
				Value Description
				0 A low-battery voltage interrupt has not occurred or is masked.
				1 An unmasked interrupt was signaled due to a low-battery voltage condition.
				This bit is cleared by writing a 1 to the LOWBAT bit in the HIBIC register.
1	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.

Bit/Field	Name	Туре	Reset	Description
0	RTCALT0	RO	0	RTC Alert 0 Masked Interrupt Status
				Value Description O An RTC match interrupt has not occurred or is masked. An unmasked interrupt was signaled due to an RTC match. This bit is cleared by writing a 1 to the RTCALTO bit in the HIBIC register.


February 20, 2013 517

Register 8: Hibernation Interrupt Clear (HIBIC), offset 0x020

This register is the interrupt write-one-to-clear register for the Hibernation module interrupt sources. Writing a 1 to a bit clears the corresponding interrupt in the **HIBRIS** register.

Hibernation Interrupt Clear (HIBIC)

Base 0x400F.C000 Offset 0x020 Type R/W1C, reset 0x0000.0000



Bit/Field	Name	Туре	Reset	Description
31:5	reserved	RO	0x0000.000	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
4	WC	R/W1C	0	Write Complete/Capable Interrupt Clear
				Writing a 1 to this bit clears the \mathtt{WC} bit in the HIBRIS and HIBMIS registers.
				Reads return the raw interrupt status.
3	EXTW	R/W1C	0	External Wake-Up Interrupt Clear
				Writing a 1 to this bit clears the EXTW bit in the HIBRIS and HIBMIS registers.
				Reads return the raw interrupt status.
2	LOWBAT	R/W1C	0	Low Battery Voltage Interrupt Clear
				Writing a 1 to this bit clears the ${\tt LOWBAT}$ bit in the \textbf{HIBRIS} and \textbf{HIBMIS} registers.
				Reads return the raw interrupt status.
1	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
0	RTCALT0	R/W1C	0	RTC Alert0 Masked Interrupt Clear
				Writing a 1 to this bit clears the ${\tt RTCALT0}$ bit in the \textbf{HIBRIS} and \textbf{HIBMIS} registers.

Reads return the raw interrupt status.

Note:

The timer interrupt source cannot be cleared if the RTC value and the HIBRTCM0 register / RTCMSS field values are equal. The match interrupt takes priority over the interrupt clear.

Register 9: Hibernation RTC Trim (HIBRTCT), offset 0x024


This register contains the value that is used to trim the RTC clock predivider. It represents the computed underflow value that is used during the trim cycle. It is represented as $0x7FFF \pm N$ clock cycles, where N is the number of clock cycles to add or subtract every 64 seconds in RTC mode.

Note: The Hibernation module registers are on the Hibernation module clock domain and have special timing requirements. Software should make use of the WRC bit in the HIBCTL register to ensure that the required timing gap has elapsed. If the WRC bit is clear, any attempted write access is ignored. See "Register Access Timing" on page 493.

Hibernation RTC Trim (HIBRTCT)

Base 0x400F.C000 Offset 0x024

Type R/W, reset 0x0000.7FFF



Bit/Field	Name	Туре	Reset	Description
31:16	reserved	RO	0x0000	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
15:0	TRIM	R/W	0x7FFF	RTC Trim Value

This value is loaded into the RTC predivider every 64 seconds in RTC counter mode. In calendar mode, the value is loaded every 60 seconds. It is used to adjust the RTC rate to account for drift and inaccuracy in the clock source. Compensation can be adjusted by software by moving the default value of 0x7FFF up or down. Moving the value up slows down the RTC and moving the value down speeds up the RTC.

Register 10: Hibernation RTC Sub Seconds (HIBRTCSS), offset 0x028

This register contains the RTC sub seconds counter and match values. The RTC value can be read by first reading the **HIBRTCC** register, reading the RTCSSC field in the **HIBRTCS** register, and then rereading the **HIBRTCC** register. If the two values for **HIBRTCC** are equal, the read is valid.

Note: The Hibernation module registers are on the Hibernation module clock domain and have special timing requirements. Software should make use of the WRC bit in the **HIBCTL** register to ensure that the required timing gap has elapsed. If the WRC bit is clear, any attempted write access is ignored. See "Register Access Timing" on page 493.

Hibernation RTC Sub Seconds (HIBRTCSS)

Base 0x400F.C000 Offset 0x028

Type R/W, reset 0x0000.0000

,,	,															
	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16
	reserved		1	1	i I				RTCSSM		1	1	1		1	
Туре	RO	R/W	R/W	R/W	R/W	R/W	R/W	R/W	R/W	R/W	R/W	R/W	R/W	R/W	R/W	R/W
Reset	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0
	15	14	13	12	11	10	9	8	7	6	5	4	3	2	1	0
	reserved		1	ı					RTCSSC		!	!			!	'
Type	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO
Reset	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0
Е	Bit/Field		Nam	ne	Tv	pe	Reset	Des	scription							

Bit/Field	Name	Type	Reset	Description
31	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
30:16	RTCSSM	R/W	0x0000	RTC Sub Seconds Match
				A write loads the value into the RTC sub seconds match register in 1/32,768 of a second increments.
				A read returns the current 1/32,768 seconds match value.
15	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
14:0	RTCSSC	RO	0x0000	RTC Sub Seconds Count

A read returns the sub second RTC count in 1/32,768 seconds.


Register 11: Hibernation Data (HIBDATA), offset 0x030-0x06F

This address space is implemented as a 16x32-bit memory (64 bytes). It can be loaded by the system processor in order to store state information and retains its state during a power cut operation as long as a battery is present. The MEMPD bit in the **HIBCTL** register must be clear in order to be able to access the **HIBDATA** registers.

Note: The Hibernation module registers are on the Hibernation module clock domain and have special timing requirements. Software should make use of the WRC bit in the HIBCTL register to ensure that the required timing gap has elapsed. If the WRC bit is clear, any attempted write access is ignored. See "Register Access Timing" on page 493.

Hibernation Data (HIBDATA)

Base 0x400F.C000 Offset 0x030-0x06F Type R/W, reset -



Bit/Field	Name	Туре	Reset	Description
31.0	RTD	R/W	_	Hibernation Module NV Data

8 Internal Memory

The LM4F232H5QC microcontroller comes with 32 KB of bit-banded SRAM, internal ROM, 256 KB of Flash memory, and 2KB of EEPROM. The Flash memory controller provides a user-friendly interface, making Flash memory programming a simple task. Flash memory is organized in 1-KB independently erasable blocks and memory protection can be applied to the Flash memory on a 2-KB block basis. The EEPROM module provides a well-defined register interface to support accesses to the EEPROM with both a random access style of read and write as well as a rolling or sequential access scheme. A password model allows the application to lock one or more EEPROM blocks to control access on 16-word boundaries.

8.1 Block Diagram

Figure 8-1 on page 522 illustrates the internal SRAM, ROM, and Flash memory blocks and control logic. The dashed boxes in the figure indicate registers residing in the System Control module.





Figure 8-1. Internal Memory Block Diagram

Figure 8-2 on page 523 illustrates the internal EEPROM block and control logic. The EEPROM block is connected to the AHB bus.





8.2 Functional Description

This section describes the functionality of the SRAM, ROM, Flash, and EEPROM memories.

Note: The μ DMA controller can transfer data to and from the on-chip SRAM. However, because the Flash memory and ROM are located on a separate internal bus, it is not possible to transfer data from the Flash memory or ROM with the μ DMA controller.

8.2.1 SRAM

The internal SRAM of the Stellaris[®] devices is located at address 0x2000.0000 of the device memory map. To reduce the number of time consuming read-modify-write (RMW) operations, ARM provides bit-banding technology in the processor. With a bit-band-enabled processor, certain regions in the memory map (SRAM and peripheral space) can use address aliases to access individual bits in a single, atomic operation. The bit-band base is located at address 0x2200.0000.

The bit-band alias is calculated by using the formula:

```
bit-band alias = bit-band base + (byte offset * 32) + (bit number * 4)
```

For example, if bit 3 at address 0x2000.1000 is to be modified, the bit-band alias is calculated as:

```
0x2200.0000 + (0x1000 * 32) + (3 * 4) = 0x2202.000C
```

With the alias address calculated, an instruction performing a read/write to address 0x2202.000C allows direct access to only bit 3 of the byte at address 0x2000.1000.

For details about bit-banding, see "Bit-Banding" on page 101.

Note: The SRAM is implemented using two 32-bit wide SRAM banks (separate SRAM arrays). The banks are partitioned such that one bank contains all even words (the even bank) and the other contains all odd words (the odd bank). A write access that is followed immediately by a read access to the same bank incurs a stall of a single clock cycle. However, a write to one bank followed by a read of the other bank can occur in successive clock cycles without incurring any delay.

8.2.2 ROM

The internal ROM of the Stellaris device is located at address 0x0100.0000 of the device memory map. Detailed information on the ROM contents can be found in the *Stellaris® ROM User's Guide*.

The ROM contains the following components:

- Stellaris Boot Loader and vector table
- Stellaris Peripheral Driver Library (DriverLib) release for product-specific peripherals and interfaces
- Advanced Encryption Standard (AES) cryptography tables
- Cyclic Redundancy Check (CRC) error detection functionality

The boot loader is used as an initial program loader (when the Flash memory is empty) as well as an application-initiated firmware upgrade mechanism (by calling back to the boot loader). The Peripheral Driver Library APIs in ROM can be called by applications, reducing Flash memory requirements and freeing the Flash memory to be used for other purposes (such as additional features in the application). Advance Encryption Standard (AES) is a publicly defined encryption standard used by the U.S. Government and Cyclic Redundancy Check (CRC) is a technique to validate if a block of data has the same contents as when previously checked.

8.2.2.1 Boot Loader Overview

The Stellaris Boot Loader is used to download code to the Flash memory of a device without the use of a debug interface. When the core is reset, the user has the opportunity to direct the core to execute the ROM Boot Loader or the application in Flash memory by using any GPIO signal in Ports A-H as configured in the **Boot Configuration (BOOTCFG)** register (see page 578).

At reset, the following sequence is performed:

- 1. The **BOOTCFG** register is read. If the EN bit is clear, the ROM Boot Loader is executed.
- 2. In the ROM Boot Loader, the status of the specified GPIO pin is compared with the specified polarity. If the status matches the specified polarity, the ROM is mapped to address 0x0000.0000 and execution continues out of the ROM Boot Loader.
- 3. If the EN bit is set or the status doesn't match the specified polarity, the data at address 0x0000.0004 is read, and if the data at this address is 0xFFF.FFF, the ROM is mapped to address 0x0000.0000 and execution continues out of the ROM Boot Loader.
- **4.** If there is data at address 0x0000.0004 that is not 0xFFF.FFF, the stack pointer (**SP**) is loaded from Flash memory at address 0x0000.0000 and the program counter (**PC**) is loaded from address 0x0000.0004. The user application begins executing.

The boot loader uses a simple packet interface to provide synchronous communication with the device. The speed of the boot loader is determined by the internal oscillator (PIOSC) frequency as it does not enable the PLL. The following serial interfaces can be used:

- UART0
- SSI0
- I²C0
- USB

The data format and communication protocol are identical for the UART0, SSI0, and I2C0 interfaces.

Note: The Flash-memory-resident version of the boot loader also supports CAN.

See the *Stellaris*® *Boot Loader User's Guide* for information on the boot loader software. The USB boot loader uses the standard Device Firmware Upgrade USB device class.

Considerations When Using the UART Boot Loader in ROM

 ${\tt U0Tx}$ is not driven by the ROM boot loader until the auto-bauding process has completed. If ${\tt U0Tx}$ is floating during this time, the receiver it is connected to may see transitions on the signal, which could be interpreted by its UART as valid characters. To handle this situation, put a pull-up or pull-down on ${\tt U0Tx}$, providing a defined state for the signal until the ROM boot loader begins driving ${\tt U0Tx}$. A pull-up is preferred as it indicates that the UART is idle, rather than a pull-down, which indicates a break condition.

8.2.2.2 Stellaris Peripheral Driver Library

The Stellaris Peripheral Driver Library contains a file called <code>driverlib/rom.h</code> that assists with calling the peripheral driver library functions in the ROM. The detailed description of each function is available in the <code>Stellaris®</code> ROM User's Guide. See the "Using the ROM" chapter of the <code>Stellaris®</code> Peripheral Driver Library User's Guide for more details on calling the ROM functions and using <code>driverlib/rom.h</code>. The <code>driverlib/rom_map.h</code> header file is also provided to aid portability when using different Stellaris devices which might have a different subset of DriverLib functions in ROM. The <code>driverlib/rom_map.h</code> header file uses build-time labels to route function calls to the ROM if those functions are available on a given device, otherwise, it routes to Flash-resident versions of the functions.

A table at the beginning of the ROM points to the entry points for the APIs that are provided in the ROM. Accessing the API through these tables provides scalability; while the API locations may change in future versions of the ROM, the API tables will not. The tables are split into two levels; the main table contains one pointer per peripheral which points to a secondary table that contains one pointer per API that is associated with that peripheral. The main table is located at 0x0100.0010, right after the Cortex-M4F vector table in the ROM.

DriverLib functions are described in detail in the Stellaris® Peripheral Driver Library User's Guide.

Additional APIs are available for graphics and USB functions, but are not preloaded into ROM. The Stellaris Graphics Library provides a set of graphics primitives and a widget set for creating graphical user interfaces on Stellaris microcontroller-based boards that have a graphical display (for more information, see the *Stellaris*® *Graphics Library User's Guide*). The Stellaris USB Library is a set of data types and functions for creating USB Device, Host or On-The-Go (OTG) applications on Stellaris microcontroller-based boards (for more information, see the *Stellaris*® *USB Library User's Guide*).

8.2.2.3 Advanced Encryption Standard (AES) Cryptography Tables

AES is a strong encryption method with reasonable performance and size. AES is fast in both hardware and software, is fairly easy to implement, and requires little memory. AES is ideal for

applications that can use pre-arranged keys, such as setup during manufacturing or configuration. Four data tables used by the XySSL AES implementation are provided in the ROM. The first is the forward S-box substitution table, the second is the reverse S-box substitution table, the third is the forward polynomial table, and the final is the reverse polynomial table. See the *Stellaris® ROM User's Guide* for more information on AES.

8.2.2.4 Cyclic Redundancy Check (CRC) Error Detection

The CRC technique can be used to validate correct receipt of messages (nothing lost or modified in transit), to validate data after decompression, to validate that Flash memory contents have not been changed, and for other cases where the data needs to be validated. A CRC is preferred over a simple checksum (e.g. XOR all bits) because it catches changes more readily. See the *Stellaris® ROM User's Guide* for more information on CRC.

8.2.3 Flash Memory

At system clock speeds of 40 MHz and below, the Flash memory is read in a single cycle. The Flash memory is organized as a set of 1-KB blocks that can be individually erased. An individual 32-bit word can be programmed to change bits from 1 to 0. In addition, a write buffer provides the ability to program 32 continuous words in Flash memory in half the time of programming the words individually. Erasing a block causes the entire contents of the block to be reset to all 1s. The 1-KB blocks are paired into sets of 2-KB blocks that can be individually protected. The protection allows blocks to be marked as read-only or execute-only, providing different levels of code protection. Read-only blocks cannot be erased or programmed, protecting the contents of those blocks from being modified. Execute-only blocks cannot be erased or programmed and can only be read by the controller instruction fetch mechanism, protecting the contents of those blocks from being read by either the controller or a debugger.

8.2.3.1 Prefetch Buffer

The Flash memory controller has a prefetch buffer that is automatically used when the CPU frequency is greater than 40 MHz. In this mode, the Flash memory operates at half of the system clock. The prefetch buffer fetches two 32-bit words per clock allowing instructions to be fetched with no wait states while code is executing linearly. The fetch buffer includes a branch speculation mechanism that recognizes a branch and avoids extra wait states by not reading the next word pair. Also, short loop branches often stay in the buffer. As a result, some branches can be executed with no wait states. Other branches incur a single wait state.

8.2.3.2 Flash Memory Protection

The user is provided two forms of Flash memory protection per 2-KB Flash memory block in four pairs of 32-bit wide registers. The policy for each protection form is controlled by individual bits (per policy per block) in the **FMPPEn** and **FMPREn** registers.

- Flash Memory Protection Program Enable (FMPPEn): If a bit is set, the corresponding block may be programmed (written) or erased. If a bit is cleared, the corresponding block may not be changed.
- Flash Memory Protection Read Enable (FMPREn): If a bit is set, the corresponding block may be executed or read by software or debuggers. If a bit is cleared, the corresponding block may only be executed, and contents of the memory block are prohibited from being read as data.

The policies may be combined as shown in Table 8-1 on page 527.

Table 8-1. Flash Memory Protection Policy Combinations

FMPPEn	FMPREn	Protection
0	0	Execute-only protection. The block may only be executed and may not be written or erased. This mode is used to protect code.
1	0	The block may be written, erased or executed, but not read. This combination is unlikely to be used.
0	1	Read-only protection. The block may be read or executed but may not be written or erased. This mode is used to lock the block from further modification while allowing any read or execute access.
1	1	No protection. The block may be written, erased, executed or read.

A Flash memory access that attempts to read a read-protected block (**FMPREn** bit is set) is prohibited and generates a bus fault. A Flash memory access that attempts to program or erase a program-protected block (**FMPPEn** bit is set) is prohibited and can optionally generate an interrupt (by setting the AMASK bit in the **Flash Controller Interrupt Mask (FCIM)** register) to alert software developers of poorly behaving software during the development and debug phases.

The factory settings for the **FMPREn** and **FMPPEn** registers are a value of 1 for all implemented banks. These settings create a policy of open access and programmability. The register bits may be changed by clearing the specific register bit. The changes are effective immediately, but are not permanent until the register is committed (saved), at which point the bit change is permanent. If a bit is changed from a 1 to a 0 and not committed, it may be restored by executing a power-on reset sequence. The changes are committed using the **Flash Memory Control (FMC)** register. Details on programming these bits are discussed in "Non-Volatile Register Programming" on page 530.

8.2.3.3 Execute-Only Protection

Execute-only protection prevents both modification and visibility to a protected flash block. This mode is intended to be used in situations where a device requires debug capability, yet portions of the application space must be protected from external access. An example of this is a company who wishes to sell Stellaris devices with their proprietary software pre-programmed, yet allow the end user to add custom code to an unprotected region of the flash (such as a motor control module with a customizable motor configuration section in flash).

Literal data introduces a complication to the protection mechanism. When C code is compiled and linked, literal data (constants, and so on) is typically placed in the text section, between functions, by the compiler. The literal data is accessed at run time through the use of the LDR instruction, which loads the data from memory using a PC-relative memory address. The execution of the LDR instruction generates a read transaction across the Cortex-M3's DCode bus, which is subject to the execute-only protection mechanism. If the accessed block is marked as execute only, the transaction is blocked, and the processor is prevented from loading the constant data and, therefore, inhibiting correct execution. Therefore, using execute-only protection requires that literal data be handled differently. There are three ways to address this:

- 1. Use a compiler that allows literal data to be collected into a separate section that is put into one or more read-enabled flash blocks. Note that the LDR instruction may use a PC-relative address—in which case the literal pool cannot be located outside the span of the offset—or the software may reserve a register to point to the base address of the literal pool and the LDR offset is relative to the beginning of the pool.
- 2. Use a compiler that generates literal data from arithmetic instruction immediate data and subsequent computation.
- 3. Use method 1 or 2, but in assembly language, if the compiler does not support either method.

8.2.3.4 Read-Only Protection

Read-only protection prevents the contents of the flash block from being re-programmed, while still allowing the content to be read by processor or the debug interface. Note that if a **FMPREn** bit is cleared, all read accesses to the Flash memory block are disallowed, including any data accesses. Care must be taken not to store required data in a Flash memory block that has the associated **FMPREn** bit cleared.

The read-only mode does not prevent read access to the stored program, but it does provide protection against accidental (or malicious) erasure or programming. Read-only is especially useful for utilities like the boot loader when the debug interface is permanently disabled. In such combinations, the boot loader, which provides access control to the Flash memory, is protected from being erased or modified.

8.2.3.5 Permanently Disabling Debug

For extremely sensitive applications, the debug interface to the processor and peripherals can be permanently disabled, blocking all accesses to the device through the JTAG or SWD interfaces. With the debug interface disabled, it is still possible to perform standard IEEE instructions (such as boundary scan operations), but access to the processor and peripherals is blocked.

The DBG0 and DBG1 bits of the **Boot Configuration (BOOTCFG)** register control whether the debug interface is turned on or off.

The debug interface should not be permanently disabled without providing some mechanism—such as the boot loader—to provide customer-installable updates or bug fixes. Disabling the debug interface is permanent and cannot be reversed.

8.2.3.6 Interrupts

The Flash memory controller can generate interrupts when the following conditions are observed:

- Programming Interrupt signals when a program or erase action is complete.
- Access Interrupt signals when a program or erase action has been attempted on a 2-kB block of memory that is protected by its corresponding FMPPEn bit.

The interrupt events that can trigger a controller-level interrupt are defined in the **Flash Controller Masked Interrupt Status (FCMIS)** register (see page 546) by setting the corresponding MASK bits. If interrupts are not used, the raw interrupt status is always visible via the **Flash Controller Raw Interrupt Status (FCRIS)** register (see page 543).

Interrupts are always cleared (for both the **FCMIS** and **FCRIS** registers) by writing a 1 to the corresponding bit in the **Flash Controller Masked Interrupt Status and Clear (FCMISC)** register (see page 548).

8.2.3.7 Flash Memory Programming

The Stellaris devices provide a user-friendly interface for Flash memory programming. All erase/program operations are handled via three registers: **Flash Memory Address (FMA)**, **Flash Memory Data (FMD)**, and **Flash Memory Control (FMC)**. Note that if the debug capabilities of the microcontroller have been deactivated, resulting in a "locked" state, a recovery sequence must be performed in order to reactivate the debug module. See "Recovering a "Locked" Microcontroller" on page 209.

During a Flash memory operation (write, page erase, or mass erase) access to the Flash memory is inhibited. As a result, instruction and literal fetches are held off until the Flash memory operation

is complete. If instruction execution is required during a Flash memory operation, the code that is executing must be placed in SRAM and executed from there while the flash operation is in progress.

Note: When programming Flash memory, the following characteristics of the memory must be considered:

- Only an erase can change bits from 0 to 1.
- A write can only change bits from 1 to 0. If the write attempts to change a 0 to a 1, the write fails and no bits are changed.
- A flash operation can be started before entering the Sleep or Deep-sleep mode (using the wait for interrupt instruction, WFI). It can also be completed while in Sleep or Deep-sleep. If the Flash program/erase event comes in succession to EEPROM access, the Flash event gets completed after waking from Sleep/Deep-sleep and is started after the wake-up.

To program a 32-bit word

- Write source data to the FMD register.
- **2.** Write the target address to the **FMA** register.
- 3. Write the Flash memory write key and the WRITE bit to the FMC register. Depending on the value of the KEY bit in the BOOTCFG register, the value 0xA442 or 0x71D5 must be written into the WRKEY field for a Flash memory write to occur.
- 4. Poll the FMC register until the WRITE bit is cleared.

To perform an erase of a 1-KB page

- 1. Write the page address to the **FMA** register.
- 2. Write the Flash memory write key and the ERASE bit to the FMC register. Depending on the value of the KEY bit in the BOOTCFG register, the value 0xA442 or 0x71D5 must be written into the WRKEY field for a Flash memory write to occur.
- **3.** Poll the **FMC** register until the ERASE bit is cleared or, alternatively, enable the programming interrupt using the PMASK bit in the **FCIM** register.

To perform a mass erase of the Flash memory

- 1. Write the Flash memory write key and the MERASE bit to the **FMC** register. Depending on the value of the KEY bit in the **BOOTCFG** register, the value 0xA442 or 0x71D5 must be written into the WRKEY field for a Flash memory write to occur.
- 2. Poll the FMC register until the MERASE bit is cleared or, alternatively, enable the programming interrupt using the PMASK bit in the FCIM register.

8.2.3.8 32-Word Flash Memory Write Buffer

A 32-word write buffer provides the capability to perform faster write accesses to the Flash memory by programming 2 32-bit words at a time, allowing 32 words to be programmed in the same time as 16 would take using the method described above. The data for the buffered write is written to the **Flash Write Buffer (FWBn)** registers.

The registers are 32-word aligned with Flash memory, and therefore the register **FWB0** corresponds with the address in **FMA** where bits [6:0] of **FMA** are all 0. **FWB1** corresponds with the address in **FMA** + 0x4 and so on. Only the **FWBn** registers that have been updated since the previous buffered Flash memory write operation are written. The **Flash Write Buffer Valid (FWBVAL)** register shows which registers have been written since the last buffered Flash memory write operation. This register contains a bit for each of the 32 **FWBn** registers, where bit[n] of **FWBVAL** corresponds to **FWBn**. The **FWBn** register has been updated if the corresponding bit in the **FWBVAL** register is set.

To program 32 words with a single buffered Flash memory write operation

- 1. Write the source data to the **FWBn** registers.
- 2. Write the target address to the **FMA** register. This must be a 32-word aligned address (that is, bits [6:0] in **FMA** must be 0s).
- 3. Write the Flash memory write key and the WRBUF bit to the FMC2 register. Depending on the value of the KEY bit in the BOOTCFG register, the value 0xA442 or 0x71D5 must be written into the WRKEY field for a Flash memory write to occur.
- 4. Poll the FMC2 register until the WRBUF bit is cleared or wait for the PMIS interrupt to be signaled.

8.2.3.9 Non-Volatile Register Programming

Note: The **Boot Configuration (BOOTCFG)** register requires a POR before the committed changes take effect.

This section discusses how to update the registers shown in Table 8-2 on page 531 that are resident within the Flash memory itself. These registers exist in a separate space from the main Flash memory array and are not affected by an ERASE or MASS ERASE operation. With the exception of the **Boot Configuration (BOOTCFG)** register, the settings in these registers can be written, their functions verified, and their values read back before they are committed, at which point they become non-volatile. If a value in one of these registers has not been committed, a power-on reset restores the last committed value or the default value if the register has never been committed. Other types of reset have no effect. Once the register contents are committed, the only way to restore the factory default values is to perform the sequence described in "Recovering a "Locked" Microcontroller" on page 209.

To write to a non-volatile register:

- Bits can only be changed from 1 to 0.
- For all registers except the **BOOTCFG** register, write the data to the register address provided in the register description. For the **BOOTCFG** register, write the data to the **FMD** register.
- The registers can be read to verify their contents. To verify what is to be stored in the **BOOTCFG** register, read the **FMD** register. Reading the **BOOTCFG** register returns the previously committed value or the default value if the register has never been committed.
- The new values are effectively immediately for all registers except **BOOTCFG**, as the new value for the register is not stored in the register until it has been committed.
- Prior to committing the register value, a power-on reset restores the last committed value or the default value if the register has never been committed.

To commit a new value to a non-volatile register:

- Write the data as described above.
- Write to the **FMA** register the value shown in Table 8-2 on page 531.
- Write the Flash memory write key and set the COMT bit in the **FMC** register. These values must be written to the **FMC** register at the same time.
- Committing a non-volatile register has the same timing as a write to regular Flash memory, defined by T_{PROG64}, as shown in Table 24-26 on page 1399. Software can poll the COMT bit in the **FMC** register to determine when the operation is complete, or an interrupt can be enabled by setting the PMASK bit in the **FCIM** register.
- When committing the **BOOTCFG** register, the INVDRIS bit in the **FCRIS** register is set if a bit that has already been committed as a 0 is attempted to be committed as a 1.
- Once the value has been committed, a power-on reset has no effect on the register contents.
- Changes to the **BOOTCFG** register are effective after the next power-on reset.
- Once the NW bit has been changed to 0 and committed, further changes to the **BOOTCFG** register are not allowed.

Important: After being committed, these registers can only be restored to their factory default values by performing the sequence described in "Recovering a "Locked" Microcontroller" on page 209. The mass erase of the main Flash memory array caused by the sequence is performed prior to restoring these registers.

Table 8-2. User-Programmable Flash Memory Resident Registers

Register to be Committed	FMA Value	Data Source
FMPRE0	0x0000.0000	FMPRE0
FMPRE1	0x0000.0002	FMPRE1
FMPRE2	0x0000.0004	FMPRE2
FMPRE3	0x0000.0006	FMPRE3
FMPPE0	0x0000.0001	FMPPE0
FMPPE1	0x0000.0003	FMPPE1
FMPPE2	0x0000.0005	FMPPE2
FMPPE3	0x0000.0007	FMPPE3
USER_REG0	0x8000.0000	USER_REG0
USER_REG1	0x8000.0001	USER_REG1
USER_REG2	0x8000.0002	USER_REG2
USER_REG3	0x8000.0003	USER_REG3
BOOTCFG	0x7510.0000	FMD

8.2.4 **EEPROM**

The LM4F232H5QC microcontroller includes an EEPROM with the following features:

- 2Kbytes of memory accessible as 512 32-bit words
- 32 blocks of 16 words (64 bytes) each

- Built-in wear leveling
- Access protection per block
- Lock protection option for the whole peripheral as well as per block using 32-bit to 96-bit unlock codes (application selectable)
- Interrupt support for write completion to avoid polling
- Endurance of 500K writes (when writing at fixed offset in every alternate page in circular fashion) to 15M operations (when cycling through two pages) per each 2-page block.

8.2.4.1 Functional Description

The EEPROM module provides a well-defined register interface to support accesses to the EEPROM with both a random access style of read and write as well as a rolling or sequential access scheme.

A protection mechanism allows locking EEPROM blocks to prevent writes under a set of circumstances as well as reads under the same or different circumstances. The password model allows the application to lock one or more EEPROM blocks to control access on 16-word boundaries.

Important: The configuration of the system clock must not be changed while an EEPROM operation is in process. Software must wait until the WORKING bit in the **EEPROM Done Status** (**EEDONE**) register is clear before making any changes to the system clock.

Blocks

There are 32 blocks of 16 words each in the EEPROM. Bytes and half-words can be read, and these accesses do not have to occur on a word boundary. The entire word is read and any unneeded data is simply ignored. They are writable only on a word basis. To write a byte, it is necessary to read the word value, modify the appropriate byte, and write the word back.

Each block is addressable as an offset within the EEPROM, using a block select register. Each word is offset addressable within the selected block.

The current block is selected by the **EEPROM Current Block (EEBLOCK)** register. The current offset is selected and checked for validity by the **EEPROM Current Offset (EEOFFSET)** register. The application may write the **EEOFFSET** register any time, and it is also automatically incremented when the **EEPROM Read-Write with Increment (EERDWRINC)** register is accessed. However, the **EERDWRINC** register does not increment the block number, but instead wraps within the block.

Blocks are individually protectable. Attempts to read from a block for which the application does not have permission return 0xFFFF.FFFF. Attempts to write into a block for which the application does not have permission results in an error in the **EEDONE** register.

Timing Considerations

After enabling or resetting the EEPROM module, software must wait until the WORKING bit in the **EEDONE** register is clear before accessing any EEPROM registers.

In the event that there are Flash memory writes or erases and EEPROM writes active, it is possible for the EEPROM process to be interrupted by the Flash memory write/erase and then continue after the Flash memory write is completed. This action may change the amount of time that the EEPROM operation takes.

EEPROM operations must be completed before entering Sleep or Deep-Sleep mode. Ensure the EEPROM operations have completed by checking the **EEPROM Done Status (EEDONE)** register before issuing a WFI instruction to enter Sleep or Deep-Sleep.

Reads of words within a block are at direct speed, which means that wait states are automatically generated if the system clock is faster than the speed of the EEPROM. The read access time is specified in Table 24-27 on page 1399.

Writing the **EEOFFSET** register also does not incur any penalties.

Writing the **EEBLOCK** register is not delayed, but any attempt to access data within that block is delayed by 4 clocks after writing **EEBLOCK**. This time is used to load block specific information.

Writes to words within a block are delayed by a variable amount of time. The application may use an interrupt to be notified when the write is done, or alternatively poll for the done status in the **EEDONE** register. The variability ranges from the write timing of the EEPROM to the erase timing of EEPROM, where the erase timing is less than the write timing of most external EEPROMs.

Locking and Passwords

The EEPROM can be locked at both the module level and the block level. The lock is controlled by a password that is stored in the **EEPROM Password (EEPASSn)** registers and can be any 32-bit to 96-bit value other than all 1s. Block 0 is the master block, the password for block 0 protects the control registers as well as all other blocks. Each block can be further protected with a password for that block.

If a password is registered for block 0, then the whole module is locked at reset. The locking behavior is such that blocks 1 to 31 are inaccessible until block 0 is unlocked, and block 0 follows the rules defined by its protection bits. As a result, the **EEBLOCK** register cannot be changed from 0 until block 0 is unlocked.

A password registered with any block, including block 0, allows for protection rules that control access of that block based on whether it is locked or unlocked. Generally, the lock can be used to prevent write accesses when locked or can prevent read and write accesses when locked.

All password-protected blocks are locked at reset. To unlock a block, the correct password value must be written to the **EEPROM Unlock** (**EEUNLOCK**) register by writing to it one to three times to form the 32-bit, 64-bit, or 96-bit password registered using the **EEPASSn** register. The value used to configure the **EEPASS0** register must always be written last. For example, for a 96-bit password, the value used to configure the **EEPASS2** register must be written first, followed by the **EEPASS1** and the **EEPASS0** register values. A block or the module may be re-locked by writing 0xFFFF.FFFF to the **EEUNLOCK** register because 0xFFFF.FFFF is not a valid password.

Protection and Access Control

The protection bits provide discrete control of read and write access for each block which allows various protection models per block, including:

- Without password: Readable and writable at any time. This mode is the default when there is no password.
- Without password: Readable but not writable.
- With password: Readable, but only writable when unlocked by the password. This mode is the default when there is a password.
- With password: Readable or writable only when unlocked.
- With password: Readable only when unlocked, not writable.

Additionally, access protection may be applied based on the processor mode. This configuration allows for supervisor-only access or supervisor and user access, which is the default. Supervisor-only access mode also prevents access by the µDMA and Debugger.

Additionally, the master block may be used to control access protection for the protection mechanism itself. If access control for block 0 is for supervisor only, then the whole module may only be accessed in supervisor mode. In addition, the protection level for block 0 sets the minimum protection level for the entire EEPROM. For example, if the PROT field in the **EEPROT** register is configured to 0x1 for block 0, then block 1 could be configured with the PROT field to be 0x1, 0x2, or 0x3, but not 0x0.

Note that for blocks 1 to 31, they are inaccessible for read or write if block 0 has a password and it is not unlocked. If block 0 has a master password, then the strictest protection defined for block 0 or an individual block is implemented on the remaining blocks.

Hidden Blocks

Hiding provides a temporary form of protection. Every block except block 0 can be hidden, which prevents all accesses until the next reset.

This mechanism can allow a boot or initialization routine to access some data which is then made inaccessible to all further accesses. Because boot and initialization routines control the capabilities of the application, hidden blocks provide a powerful isolation of the data when debug is disabled.

A typical use model would be to have the initialization code store passwords, keys, and/or hashes to use for verification of the rest of the application. Once performed, the block is then hidden and made inaccessible until the next reset which then re-enters the initialization code.

Power and Reset Safety

Once the **EEDONE** register indicates that a location has been successfully written, the data is retained until that location is written again. There is no power or reset race after the **EEDONE** register indicates a write has completed.

Interrupt Control

The EEPROM module allows for an interrupt when a write completes to eliminate the need for polling. The interrupt can be used to drive an application ISR which can then write more words or verify completion. The interrupt mechanism is used any time the **EEDONE** register goes from working to done, whether because of an error or the successful completion of a program or erase operation. This interrupt mechanism works for data writes, writes to password and protection registers, forced erase by the **EEPROM Support Control and Status (EESUPP)** register, and mass erase using the **EEPROM Debug Mass Erase (EEDGBME)** register. The EEPROM interrupt is signaled to the core using the Flash memory interrupt vector. Software can determine that the source of the interrupt was the EEPROM by examining bit 2 of the **Flash Controller Masked Interrupt Status and Clear (FCMISC)** register.

Theory of Operation

The EEPROM operates using a traditional Flash bank model which implements EEPROM-type cells, but uses sector erase. Additionally, words are replicated in the pages to allow 500K+ erase cycles when needed, which means that each word has a latest version. As a result, a write creates a new version of the word in a new location, making the previous value obsolete.

Each sector contains two blocks. Each block contains locations for the active copy plus six redundant copies. Passwords, protection bits, and control data are all stored in the pages.

When a page runs out of room to store the latest version of a word, a copy buffer is used. The copy buffer copies the latest words of each block. The original page is then erased. Finally, the copy

buffer contents are copied back to the page. This mechanism ensures that data cannot be lost due to power down, even during an operation. The EEPROM mechanism properly tracks all state information to provide complete safety and protection. Although it should not normally be possible, errors during programming can occur in certain circumstances, for example, the voltage rail dropping during programming. In these cases, the **EESUPP** register can be used to finish an operation as described in the section called "Error During Programming" on page 535.

Manual Copy Buffer Erase

The copy buffer is only used when a main block is full because a word has been written seven times and there is no more room to store its latest version. In this situation, the latest versions of all the words in the block are copied to the copy buffer, allowing the main block to be erased safely, providing power down safety. If the copy buffer itself is full, then it must first be erased, which adds extra time. By performing a manual erase of the copy buffer, this overhead does not occur during a future write access. The EREQ bit in the **EESUPP** register is set if the copy buffer must be erased. If so, the START bit can be written by the application to force the erase at a more convenient time. The **EEDONE** and **EEINT** registers can be used to detect completion.

Debug Mass Erase

The EEPROM debug mass erase allows the developer to mass erase the EEPROM. For the mass erase to occur correctly, there can be no active EEPROM operations. After the last EEPROM operation, the application must ensure that no EEPROM registers are updated, including modifying the **EEBLOCK** and the **EEOFFSET** registers without doing an actual read or write operation. To hold off these operations, the application should reset the EEPROM module by setting the R0 bit in the **EEPROM Software Reset (SREEPROM)** register, wait until WORKING bit in the **EEPROM Done Status (EEDONE)** register is clear, and then enable the debug mass erase by setting the ME bit in the **EEPROM Debug Mass Erase (EEDBGME)** register.

Error During Programming

Operations such as data-write, password set, protection set, and copy buffer erase may perform multiple operations. For example, a normal write performs two underlying writes: the control word write and the data write. If the control word writes but the data fails (for example, due to a voltage drop), the overall write fails with indication provided in the **EEDONE** register. Failure and the corrective action is broken down by the type of operation:

- If a normal write fails such that the control word is written but the data fails to write, the safe course of action is to retry the operation once the system is otherwise stable, for example, when the voltage is stabilized. After the retry, the control word and write data are advanced to the next location.
- If a password or protection write fails, the safe course of action is to retry the operation once the system is otherwise stable. In the event that multi-word passwords may be written outside of a manufacturing or bring-up mode, care must be taken to ensure all words are written in immediate succession. If not, then partial password unlock would need to be supported to recover.
- If the word write requires the block to be written to the copy buffer, then it is possible to fail or lose power during the subsequent operations. A control word mechanism is used to track what step the EEPROM was in if a failure occurs. If not completed, the EESUPP register indicates the partial completion, and the EESUPP START bit can be written to allow it to continue to completion.
- If a copy buffer erase fails or power is lost while erasing, the **EESUPP** register indicates it is not complete and allows it to be restarted

After a reset and prior to writing any data to the EEPROM, software must read the **EESUPP** register and check for the presence of any error condition which may indicate that a write or erase was in progress when the system was reset due to a voltage drop. If either the PRETRY or ERETRY bits are set, the peripheral should be reset by setting and then clearing the R0 bit in the **EEPROM Software Reset (SREEPROM)** register and waiting for the WORKING bit in the **EEDONE** register to clear before again checking the **EESUPP** register for error indicators. This procedure should allow the EEPROM to recover from the write or erase error. In very isolated cases, the **EESUPP** register may continue to register an error after this operation, in which case the reset should be repeated. After recovery, the application should rewrite the data which was being programmed when the initial failure occurred.

Endurance

Endurance is per meta-block which is 2 blocks. Endurance is measured in two ways:

- 1. To the application, it is the number of writes that can be performed.
- 2. To the microcontroller, it is the number of erases that can be performed on the meta-block.

Because of the second measure, the number of writes depends on how the writes are performed. For example:

- One word can be written more than 500K times, but, these writes impact the meta-block that the word is within. As a result, writing one word 500K times, then trying to write a nearby word 500K times is not assured to work. To ensure success, the words should be written more in parallel.
- All words can be written in a sweep with a total of more than 500K sweeps which updates all words more than 500K times.
- Different words can be written such that any or all words can be written more than 500K times when write counts per word stay about the same. For example, offset 0 could be written 3 times, then offset 1 could be written 2 times, then offset 2 is written 4 times, then offset 1 is written twice, then offset 0 is written again. As a result, all 3 offsets would have 4 writes at the end of the sequence. This kind of balancing within 7 writes maximizes the endurance of different words within the same meta-block.

8.2.4.2 **EEPROM Initialization and Configuration**

Before writing to any EEPROM registers, the clock to the EEPROM module must be enabled, see page 347.

A common setup is as follows:

- Block 0 has a password.
- Block 0 is readable by all, but only writable when unlocked.
- Block 0 has an ID and other public data.

In this configuration, the ID is readable any time, but the rest of the EEPROM is locked to accesses by the application. The rest of the blocks only become available when parts of the application that are allowed to access the EEPROM choose to unlock block 0.

8.3 Register Map

Table 8-3 on page 537 lists the ROM Controller register and the Flash memory and control registers. The offset listed is a hexadecimal increment to the particular memory controller's base address. The Flash memory register offsets are relative to the Flash memory control base address of 0x400F.D000. The EEPROM registers are relative to the EEPROM base address of 0x400A.F000. The ROM and Flash memory protection register offsets are relative to the System Control base address of 0x400F.E000.

Table 8-3. Flash Register Map

Offset	Name	Туре	Reset	Description	See page
Flash Mer	nory Registers (Flash	Control Offse	et)		
0x000	FMA	R/W	0x0000.0000	Flash Memory Address	539
0x004	FMD	R/W	0x0000.0000	Flash Memory Data	540
0x008	FMC	R/W	0x0000.0000	Flash Memory Control	541
0x00C	FCRIS	RO	0x0000.0000	Flash Controller Raw Interrupt Status	543
0x010	FCIM	R/W	0x0000.0000	Flash Controller Interrupt Mask	546
0x014	FCMISC	R/W1C	0x0000.0000	Flash Controller Masked Interrupt Status and Clear	548
0x020	FMC2	R/W	0x0000.0000	Flash Memory Control 2	551
0x030	FWBVAL	R/W	0x0000.0000	Flash Write Buffer Valid	552
0x100 - 0x17C	FWBn	R/W	0x0000.0000	Flash Write Buffer n	553
0xFC0	FSIZE	RO	0x0000.007F	Flash Size	554
0xFC4	SSIZE	RO	0x0000.007F	SRAM Size	555
0xFCC	ROMSWMAP	RO	0x0000.0000	ROM Software Map	556
EEPROM	Registers (EEPROM C	Control Offset)		
0x000	EESIZE	RO	0x0020.0200	EEPROM Size Information	557
0x004	EEBLOCK	R/W	0x0000.0000	EEPROM Current Block	558
0x008	EEOFFSET	R/W	0x0000.0000	EEPROM Current Offset	559
0x010	EERDWR	R/W	-	EEPROM Read-Write	560
0x014	EERDWRINC	R/W	-	EEPROM Read-Write with Increment	561
0x018	EEDONE	RO	0x0000.0000	EEPROM Done Status	562
0x01C	EESUPP	R/W	-	EEPROM Support Control and Status	564
0x020	EEUNLOCK	R/W	-	EEPROM Unlock	566
0x030	EEPROT	R/W	0x0000.0000	EEPROM Protection	567
0x034	EEPASS0	R/W	-	EEPROM Password	569
0x038	EEPASS1	R/W	-	EEPROM Password	569
0x03C	EEPASS2	R/W	-	EEPROM Password	569

Table 8-3. Flash Register Map (continued)

Offset	Name	Туре	Reset	Description	See page
0x040	EEINT	R/W	0x0000.0000	EEPROM Interrupt	570
0x050	EEHIDE	R/W	0x0000.0000	EEPROM Block Hide	571
0x080	EEDBGME	R/W	0x0000.0000	EEPROM Debug Mass Erase	572
0xFC0	EEPROMPP	RO	0x0000.001F	EEPROM Peripheral Properties	573
Memory F	Registers (System Contro	ol Offset)			
0x0F0	RMCTL	R/W1C	-	ROM Control	574
0x130	FMPRE0	R/W	0xFFFF.FFFF	Flash Memory Protection Read Enable 0	575
0x200	FMPRE0	R/W	0xFFFF.FFFF	Flash Memory Protection Read Enable 0	575
0x134	FMPPE0	R/W	0xFFFF.FFFF	Flash Memory Protection Program Enable 0	576
0x400	FMPPE0	R/W	0xFFFF.FFFF	Flash Memory Protection Program Enable 0	576
0x1D0	BOOTCFG	RO	0xFFFF.FFFE	Boot Configuration	578
0x1E0	USER_REG0	R/W	0xFFFF.FFFF	User Register 0	581
0x1E4	USER_REG1	R/W	0xFFFF.FFFF	User Register 1	581
0x1E8	USER_REG2	R/W	0xFFFF.FFFF	User Register 2	581
0x1EC	USER_REG3	R/W	0xFFFF.FFFF	User Register 3	581
0x204	FMPRE1	R/W	0xFFFF.FFFF	Flash Memory Protection Read Enable 1	575
0x208	FMPRE2	R/W	0xFFFF.FFFF	Flash Memory Protection Read Enable 2	575
0x20C	FMPRE3	R/W	0xFFFF.FFFF	Flash Memory Protection Read Enable 3	575
0x404	FMPPE1	R/W	0xFFFF.FFFF	Flash Memory Protection Program Enable 1	576
0x408	FMPPE2	R/W	0xFFFF.FFFF	Flash Memory Protection Program Enable 2	576
0x40C	FMPPE3	R/W	0xFFFF.FFFF	Flash Memory Protection Program Enable 3	576

8.4 Flash Memory Register Descriptions (Flash Control Offset)

This section lists and describes the Flash Memory registers, in numerical order by address offset. Registers in this section are relative to the Flash control base address of 0x400F.D000.


Register 1: Flash Memory Address (FMA), offset 0x000

During a single word write operation, this register contains a 4-byte-aligned address and specifies where the data is written. During a write operation that uses the write buffer, this register contains a 128-byte (32-word) aligned address that specifies the start of the 32-word block to be written. During erase operations, this register contains a 1 KB-aligned CPU byte address and specifies which block is erased. Note that the alignment requirements must be met by software or the results of the operation are unpredictable.

Flash Memory Address (FMA)

Base 0x400F.D000 Offset 0x000

Type R/W, reset 0x0000.0000



Bit/Field	Name	Type	Reset	Description
31:18	reserved	RO	0x0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
17:0	OFFSET	R/W	0x0	Address Offset


Address offset in Flash memory where operation is performed, except for non-volatile registers (see "Non-Volatile Register Programming" on page 530 for details on values for this field).

Register 2: Flash Memory Data (FMD), offset 0x004

This register contains the data to be written during the programming cycle. This register is not used during erase cycles.

Flash Memory Data (FMD)

Base 0x400F.D000 Offset 0x004 Type R/W, reset 0x0000.0000



31:0 DATA R/W 0x0000.0000 Data Value

Data value for write operation.

Register 3: Flash Memory Control (FMC), offset 0x008

When this register is written, the Flash memory controller initiates the appropriate access cycle for the location specified by the **Flash Memory Address (FMA)** register (see page 539). If the access is a write access, the data contained in the **Flash Memory Data (FMD)** register (see page 540) is written to the specified address.

This register must be the final register written and initiates the memory operation. The four control bits in the lower byte of this register are used to initiate memory operations.

Care must be taken not to set multiple control bits as the results of such an operation are unpredictable.

Flash Memory Control (FMC)

Name


Type

Pasat

Base 0x400F.D000 Offset 0x008

Rit/Field

Type R/W, reset 0x0000.0000



Bit/Field	name	туре	Reset	Description
31:16	WRKEY	WO	0x0000	Flash Memory Write Key
				This field contains a write key, which is used to minimize the incidence of accidental Flash memory writes. Depending on the value of the KEY bit in the BOOTCFG register, the value 0xA442 or 0x71D5 must be written into this field for a Flash memory write to occur. Writes to the FMC register without this WRKEY value are ignored. A read of this field returns the value 0.
15:4	reserved	RO	0x00	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
3	COMT	R/W	0	Commit Register Value

Description

This bit is used to commit writes to Flash-memory-resident registers

and to monitor the progress of that process.

Value Description

- 0 A write of 0 has no effect on the state of this bit.
 When read, a 0 indicates that the previous commit access is complete.
- Set this bit to commit (write) the register value to a Flash-memory-resident register.

When read, a 1 indicates that the previous commit access is not complete.

See "Non-Volatile Register Programming" on page 530 for more information on programming Flash-memory-resident registers.

Bit/Field	Name	Туре	Reset	Description
2	MERASE	R/W	0	Mass Erase Flash Memory
				This bit is used to mass erase the Flash main memory and to monitor the progress of that process.
				Value Description
				0 A write of 0 has no effect on the state of this bit.
				When read, a 0 indicates that the previous mass erase operation is complete.
				1 Set this bit to erase the Flash main memory.
				When read, a 1 indicates that the previous mass erase operation is not complete.
				For information on erase time, see "Flash Memory and EEPROM" on page 1399.
1	ERASE	R/W	0	Erase a Page of Flash Memory
				This bit is used to erase a page of Flash memory and to monitor the progress of that process.
				Value Description
				0 A write of 0 has no effect on the state of this bit.
				When read, a 0 indicates that the previous page erase operation is complete.
				Set this bit to erase the Flash memory page specified by the contents of the FMA register.
				When read, a 1 indicates that the previous page erase operation is not complete.
				For information on erase time, see "Flash Memory and EEPROM" on page 1399.
0	WRITE	R/W	0	Write a Word into Flash Memory
				This bit is used to write a word into Flash memory and to monitor the progress of that process.
				Value Description
				0 A write of 0 has no effect on the state of this bit.
				When read, a 0 indicates that the previous write update operation is complete.
				Set this bit to write the data stored in the FMD register into the Flash memory location specified by the contents of the FMA register.
				When read, a 1 indicates that the write update operation is not complete.
				For information on programming time, see "Flash Memory and EEPROM" on page 1399.

Register 4: Flash Controller Raw Interrupt Status (FCRIS), offset 0x00C

This register indicates that the Flash memory controller has an interrupt condition. An interrupt is sent to the interrupt controller only if the corresponding **FCIM** register bit is set.

Flash Controller Raw Interrupt Status (FCRIS)

ERRIS


11

RO

0

Base 0x400F.D000

Offset 0x00C Type RO, reset 0x0000.0000



Bit/Field	Name	Туре	Reset	Description
31:14	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
13	PROGRIS	RO	0	Program Verify Error Raw Interrupt Status
				Value Description
				0 An interrupt has not occurred.
				An interrupt is pending because the verify of a PROGRAM operation failed. If this error occurs when using the Flash write buffer, software must inspect the affected words to determine where the error occurred.
				This bit is cleared by writing a 1 to the PROGMISC bit in the FCMISC register.
12	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.

Value Description

0 An interrupt has not occurred.

Erase Verify Error Raw Interrupt Status

An interrupt is pending because the verify of an ERASE operation failed. If this error occurs when using the Flash write buffer, software must inspect the affected words to determine where the error occurred.

This bit is cleared by writing a 1 to the ERMISC bit in the FCMISC register.

Bit/Field	Name	Туре	Reset	Description
10	INVDRIS	RO	0	Invalid Data Raw Interrupt Status
				Value Description
				0 An interrupt has not occurred.
				An interrupt is pending because a bit that was previously programmed as a 0 is now being requested to be programmed as a 1.
				This bit is cleared by writing a 1 to the INVMISC bit in the FCMISC register.
9	VOLTRIS	RO	0	Pump Voltage Raw Interrupt Status
				Value Description
				0 An interrupt has not occurred.
				An interrupt is pending because the regulated voltage of the pump went out of spec during the Flash operation and the operation was terminated.
				This bit is cleared by writing a 1 to the <code>VOLTMISC</code> bit in the FCMISC register.
8:3	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
2	ERIS	RO	0	EEPROM Raw Interrupt Status
				This bit provides status EEPROM operation.
				Value Description
				An EEPROM interrupt has not occurred.
				1 An EEPROM interrupt has occurred.
				This bit is cleared by writing a 1 to the EMISC bit in the FCMISC register.
1	PRIS	RO	0	Programming Raw Interrupt Status
				This bit provides status on programming cycles which are write or erase actions generated through the FMC or FMC2 register bits (see page 541 and page 551).
				Value Description
				The programming or erase cycle has not completed.
				1 The programming or erase cycle has completed.
				This status is sent to the interrupt controller when the PMASK bit in the FCIM register is set.
				This bit is cleared by writing a 1 to the PMISC bit in the FCMISC register.

This bit is cleared by writing a 1 to the ${\tt AMISC}$ bit in the ${\tt FCMISC}$ register.

Bit/Field	Name	Туре	Reset	Description
0	ARIS	RO	0	Access Raw Interrupt Status
				Value Description
				No access has tried to improperly program or erase the Flash memory.
				A program or erase action was attempted on a block of Flash memory that contradicts the protection policy for that block as set in the FMPPEn registers.
				This status is sent to the interrupt controller when the AMASK bit in the FCIM register is set.

February 20, 2013 545


Register 5: Flash Controller Interrupt Mask (FCIM), offset 0x010

This register controls whether the Flash memory controller generates interrupts to the controller.

Flash Controller Interrupt Mask (FCIM)

Base 0x400F.D000 Offset 0x010

Type R/W, reset 0x0000.0000



Bit/Field	Name	Type	Reset	Description
31:14	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
13	PROGMASK	R/W	0	PROGVER Interrupt Mask
				Value Description
				The PROGRIS interrupt is suppressed and not sent to the interrupt controller.
				An interrupt is sent to the interrupt controller when the PROGRIS bit is set.
12	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
11	ERMASK	R/W	0	ERVER Interrupt Mask
				Value Description
				O The ERRIS interrupt is suppressed and not sent to the interrupt controller.
				An interrupt is sent to the interrupt controller when the ERRIS bit is set.
10	INVDMASK	R/W	0	Invalid Data Interrupt Mask
				Value Description

- 0 The INVDRIS interrupt is suppressed and not sent to the interrupt controller.
- 1 An interrupt is sent to the interrupt controller when the INVDRIS bit is set.

Bit/Field	Name	Туре	Reset	Description
9	VOLTMASK	R/W	0	VOLT Interrupt Mask
				Value Description
				0 The VOLTRIS interrupt is suppressed and not sent to the interrupt controller.
				An interrupt is sent to the interrupt controller when the VOLTRIS bit is set.
8:3	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
2	EMASK	R/W	0	EEPROM Interrupt Mask
				Value Description
				O The ERIS interrupt is suppressed and not sent to the interrupt controller.
				An interrupt is sent to the interrupt controller when the ERIS bit is set.
1	PMASK	R/W	0	Programming Interrupt Mask
				This bit controls the reporting of the programming raw interrupt status to the interrupt controller.
				Value Description
				O The PRIS interrupt is suppressed and not sent to the interrupt controller.
				An interrupt is sent to the interrupt controller when the PRIS bit is set.
0	AMASK	R/W	0	Access Interrupt Mask
				This bit controls the reporting of the access raw interrupt status to the interrupt controller.
				Value Description
				The ARIS interrupt is suppressed and not sent to the interrupt controller.
				An interrupt is sent to the interrupt controller when the ARIS bit is set.

February 20, 2013 547

Register 6: Flash Controller Masked Interrupt Status and Clear (FCMISC), offset 0x014

This register provides two functions. First, it reports the cause of an interrupt by indicating which interrupt source or sources are signalling the interrupt. Second, it serves as the method to clear the interrupt reporting.

Flash Controller Masked Interrupt Status and Clear (FCMISC)

Base 0x400F.D000 Offset 0x014
Type R/W1C, reset 0x0000.0000

_	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16
	,							rese	rved							
Type Reset	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0
. 10001	15	14	13	12	11	10	9	8	7	6	5	4	3	2	1	0
[rese		PROGMISC	reserved	ERMISC	INVDMISC	VOLTMISC			rese				EMISC	PMISC	AMISC
[Туре	RO	RO	R/W1C	RO	R/W1C	R/W1C	R/W1C	RO	RO	RO	RO	RO	RO	R/W1C	R/W1C	R/W1C
Reset	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0
В	sit/Field		Nam	ne	Ту	ре	Reset	Des	cription							
	31:14		reserv	ved	R	0	0	com	patibility	with futu	ıre prodı	he value ucts, the dify-write	value of	a reserv		
	13		PROG	MISC	R/W	/1C	0	PRO	GVER I	Masked I	nterrupt	Status a	nd Clea	r		
								Valu	ie Desc	ription						
								0	Wher	n read, a	0 indica	ates that	an interr	upt has	not occu	rred.
									A wri	te of 0 ha	as no ef	fect on th	e state	of this bit	t.	
								1	Wher signa	-	1 indica	ates that	an unma	asked int	errupt w	as
										•		clears PR ter (see p			o the PR	OGRIS
	12		reserv	ved .	R	0	0	com	patibility	with futu	ıre prodı	he value ucts, the dify-write	value of	a reserv		
	11		ERMI	sc	R/W	/1C	0	ERV	'ER Mas	ked Inte	rrupt Sta	itus and	Clear			

Value Description

- When read, a 0 indicates that an interrupt has not occurred.
 - A write of 0 has no effect on the state of this bit.
- When read, a 1 indicates that an unmasked interrupt was

Writing a 1 to this bit clears ERMISC and also the ERRIS bit in the FCRIS register (see page 543).

Bit/Field	Name	Туре	Reset	Description
10	INVDMISC	R/W1C	0	Invalid Data Masked Interrupt Status and Clear
				Value Description
				0 When read, a 0 indicates that an interrupt has not occurred.
				A write of 0 has no effect on the state of this bit.
				When read, a 1 indicates that an unmasked interrupt was signaled.
				Writing a 1 to this bit clears INVDMISC and also the INVDRIS bit in the FCRIS register (see page 543).
9	VOLTMISC	R/W1C	0	VOLT Masked Interrupt Status and Clear
				Value Description
				0 When read, a 0 indicates that an interrupt has not occurred.
				A write of 0 has no effect on the state of this bit.
				When read, a 1 indicates that an unmasked interrupt was signaled.
				Writing a 1 to this bit clears VOLTMISC and also the VOLTRIS bit in the FCRIS register (see page 543).
8:3	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
2	EMISC	R/W1C	0	EEPROM Masked Interrupt Status and Clear
				Value Description
				0 When read, a 0 indicates that an interrupt has not occurred.
				A write of 0 has no effect on the state of this bit.
				When read, a 1 indicates that an unmasked interrupt was signaled.
				Writing a 1 to this bit clears EMISC and also the ERIS bit in the FCRIS register (see page 543).
1	PMISC	R/W1C	0	Programming Masked Interrupt Status and Clear
				Value Description
				When read, a 0 indicates that a programming cycle complete interrupt has not occurred.
				A write of 0 has no effect on the state of this bit.
				When read, a 1 indicates that an unmasked interrupt was signaled because a programming cycle completed.
				Writing a 1 to this bit clears PMISC and also the PRIS bit in the FCRIS register (see page 543).

February 20, 2013 549

Bit/Field	Name	Туре	Reset	Description
0	AMISC	R/W1C	0	Access Masked Interrupt Status and Clear
				Value Description
				When read, a 0 indicates that no improper accesses have occurred.
				A write of 0 has no effect on the state of this bit.
				When read, a 1 indicates that an unmasked interrupt was signaled because a program or erase action was attempted on a block of Flash memory that contradicts the protection policy for that block as set in the FMPPEn registers.
				Writing a 1 to this bit clears ${\tt AMISC}$ and also the ${\tt ARIS}$ bit in the FCRIS register (see page 543).

Register 7: Flash Memory Control 2 (FMC2), offset 0x020


When this register is written, the Flash memory controller initiates the appropriate access cycle for the location specified by the **Flash Memory Address (FMA)** register (see page 539). If the access is a write access, the data contained in the **Flash Write Buffer (FWB)** registers is written.

This register must be the final register written as it initiates the memory operation.

Flash Memory Control 2 (FMC2)

Base 0x400F.D000 Offset 0x020

Type R/W, reset 0x0000.0000



Bit/Field	Name	Type	Reset	Description
31:16	WRKEY	WO	0x0000	Flash Memory Write Key
				This field contains a write key, which is used to minimize the incidence of accidental Flash memory writes. Depending on the value of the KEY bit in the BOOTCFG register, the value 0xA442 or 0x71D5 must be written into this field for a Flash memory write to occur. Writes to the FMC2 register without this WRKEY value are ignored. A read of this field returns the value 0.
15:1	reserved	RO	0x000	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
0	WRBUF	R/W	0	Buffered Flash Memory Write

Value Description

O A write of 0 has no effect on the state of this bit.
When read, a 0 indicates that the previous buffered Flash memory write access is complete.

This bit is used to start a buffered write to Flash memory.

Set this bit to write the data stored in the FWBn registers to the location specified by the contents of the FMA register.
When read, a 1 indicates that the previous buffered Flash memory write access is not complete.

For information on programming time, see "Flash Memory and EEPROM" on page 1399.

Register 8: Flash Write Buffer Valid (FWBVAL), offset 0x030


This register provides a bitwise status of which **FWBn** registers have been written by the processor since the last write of the Flash memory write buffer. The entries with a 1 are written on the next write of the Flash memory write buffer. This register is cleared after the write operation by hardware. A protection violation on the write operation also clears this status.

Software can program the same 32 words to various Flash memory locations by setting the FWB[n] bits after they are cleared by the write operation. The next write operation then uses the same data as the previous one. In addition, if a **FWBn** register change should not be written to Flash memory, software can clear the corresponding FWB[n] bit to preserve the existing data when the next write operation occurs.

Flash Write Buffer Valid (FWBVAL)

Base 0x400F.D000 Offset 0x030

Type R/W, reset 0x0000.0000



Value Description


- The corresponding **FWBn** register has no new data to be written.
- The corresponding FWBn register has been updated since the last buffer write operation and is ready to be written to Flash memory.

Bit 0 corresponds to **FWB0**, offset 0x100, and bit 31 corresponds to **FWB31**, offset 0x13C.

Register 9: Flash Write Buffer n (FWBn), offset 0x100 - 0x17C

These 32 registers hold the contents of the data to be written into the Flash memory on a buffered Flash memory write operation. The offset selects one of the 32-bit registers. Only **FWBn** registers that have been updated since the preceding buffered Flash memory write operation are written into the Flash memory, so it is not necessary to write the entire bank of registers in order to write 1 or 2 words. The **FWBn** registers are written into the Flash memory with the **FWB0** register corresponding to the address contained in **FMA**. **FWB1** is written to the address **FMA**+0x4 etc. Note that only data bits that are 0 result in the Flash memory being modified. A data bit that is 1 leaves the content of the Flash memory bit at its previous value.

Data to be written into the Flash memory.




Register 10: Flash Size (FSIZE), offset 0xFC0

This register indicates the size of the on-chip Flash memory.

Important: This register should be used to determine the size of the Flash memory that is implemented on this microcontroller. However, to support legacy software, the DC0 register is available. A read of the DC0 register correctly identifies legacy memory sizes. Software must use the FSIZE register for memory sizes that are not listed in the DC0 register description.

Flash Size (FSIZE)
Base 0x400F.D000
Offset 0xFC0
Type RO, reset 0x0000.007F



Bit/Field	Name	Type	Reset	Description
31:16	reserved	RO	0x0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
15:0	SIZE	RO	0x7F	Flash Size

Indicates the size of the on-chip Flash memory.

Value Description

0x0003 8 KB of Flash

0x0007 16 KB of Flash

0x000F 32 KB of Flash

0x001F 64 KB of Flash

0x002F 96 KB of Flash

0x003F 128 KB of Flash

0x005F 192 KB of Flash

0x007F 256 KB of Flash

Register 11: SRAM Size (SSIZE), offset 0xFC4


This register indicates the size of the on-chip SRAM.

Important: This register should be used to determine the size of the SRAM that is implemented on this microcontroller. However, to support legacy software, the **DC0** register is available. A read of the **DC0** register correctly identifies legacy memory sizes. Software must use the **SSIZE** register for memory sizes that are not listed in the **DC0** register description.

SRAM Size (SSIZE)

Base 0x400F.D000 Offset 0xFC4

Type RO, reset 0x0000.007F



Bit/Field	Name	Type	Reset	Description
31:16	reserved	RO	0x0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
15:0	SIZE	RO	0x7F	SRAM Size

Indicates the size of the on-chip SRAM.

Value Description

0x0007 2 KB of SRAM

0x000F 4 KB of SRAM

0x0017 6 KB of SRAM

0x001F 8 KB of SRAM

0x002F 12 KB of SRAM

0x003F 16 KB of SRAM

0x004F 20 KB of SRAM

0x005F 24 KB of SRAM

0x007F 32 KB of SRAM


Register 12: ROM Software Map (ROMSWMAP), offset 0xFCC

This register indicates the presence of third-party software in the on-chip ROM.

Important: This register should be used to determine the presence of third-party software in the on-chip ROM on this microcontroller. However, to support legacy software, the NVMSTAT register is available. A read of the TPSW bit in the NVMSTAT register correctly identifies the presence of legacy third-party software. Software should use the ROMSWMAP register for software that is not on legacy devices.



Base 0x400F.D000 Offset 0xFCC Type RO, reset 0x0000.0000



Bit/Field	Name	Type	Reset	Description
31:1	reserved	RO	0x0000	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
0	SAFERTOS	RO	0x0	SafeRTOS Present

Value Description

0 SafeRTOS is not in the on-chip ROM.

1 SafeRTOS is in the on-chip ROM.

8.5 EEPROM Register Descriptions (EEPROM Offset)

This section lists and describes the EEPROM registers, in numerical order by address offset. Registers in this section are relative to the EEPROM base address of 0x400A.F000.

Note that the EEPROM module clock must be enabled before the registers can be programmed (see page 347). There must be a delay of 3 system clocks after the EEPROM module clock is enabled before any EEPROM module registers are accessed. In addition, after enabling or resetting the EEPROM module, software must wait until the WORKING bit in the **EEDONE** register is clear before accessing any EEPROM registers.


Register 13: EEPROM Size Information (EESIZE), offset 0x000

The **EESIZE** register indicates the number of 16-word blocks and 32-bit words in the EEPROM.

EEPROM Size Information (EESIZE)

Base 0x400A.F000 Offset 0x000

Type RO, reset 0x0020.0200



Bit/Field	Name	Type	Reset	Description
31:27	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
26:16	BLKCNT	RO	0x20	Number of 16-Word Blocks
				This value encoded in this field describes the number of 16-word blocks in the EEPROM.
15:0	WORDCNT	RO	0x200	Number of 32-Bit Words

This value encoded in this field describes the number of 32-bit words in the EEPROM.


Register 14: EEPROM Current Block (EEBLOCK), offset 0x004

The **EEBLOCK** register is used to select the EEPROM block for subsequent reads, writes, and protection control. The value is a block offset into the EEPROM, such that the first block is 0, then second block is 1, etc. Each block contains 16 words. Attempts to set an invalid block causes the BLOCK field to be configured to 0. To verify that the intended block is being accessed, software can read the BLOCK field after it has been written. An invalid block can be either a non-existent block or a block that has been hidden using the **EEHIDE** register. Note that block 0 cannot be hidden.

EEPROM Current Block (EEBLOCK)

Base 0x400A.F000 Offset 0x004

Type R/W, reset 0x0000.0000



Bit/Field	Name	Type	Reset	Description
31:16	reserved	RO	0x00000	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
15:0	BLOCK	R/W	0x0000	Current Block

Current Block

This field specifies the block in the EEPROM that is selected for subsequent accesses. Once this field is configured, the read-write registers operate against the specified block, using the EEOFFSET register to select the word within the block. Additionally, the protection and unlock registers are used for the selected block. The maximum value that can be written into this register is determined by the block count, as indicated by the **EESIZE** register. Attempts to write this field larger than the maximum number of blocks or to a locked block causes this field to be configured to 0.


Register 15: EEPROM Current Offset (EEOFFSET), offset 0x008

The **EEOFFSET** register is used to select the EEPROM word to read or write within the block selected by the **EEBLOCK** register. The value is a word offset into the block. Because accesses to the **EERDWRINC** register change the offset, software can read the contents of this register to determine the current offset.

EEPROM Current Offset (EEOFFSET)

Base 0x400A.F000

Offset 0x008
Type R/W, reset 0x0000.0000



В	it/Field	Name	Type	Reset	Description
	31:4	reserved	RO	0x0000.000	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
	3:0	OFFSET	R/W	0x0	Current Address Offset

This value is the current address specified as an offset into the block selected by the **EEBLOCK** register. Once configured, the read-write registers, **EERDRWR** and **EERDWRINC**, operate against that address. The offset is automatically incremented by the **EERDWRINC** register, with wrap around within the block, which means the offset is incremented from 15 back to 0.

Register 16: EEPROM Read-Write (EERDWR), offset 0x010


The **EERDWR** register is used to read or write the EEPROM word at the address pointed to by the **EEBLOCK** and **EEOFFSET** registers. If the protection or access rules do not permit access, the operation is handled as follows: if reading is not allowed, the value 0xFFFF.FFFF is returned in all cases; if writing is not allowed, the **EEDONE** register is configured to indicate an error.

EEPROM Read-Write (EERDWR)

VALUE

Base 0x400A.F000 Offset 0x010 Type R/W, reset -

31:0



R/W - EEPROM Read or Write Data


On a read, this field contains the value at the word pointed to by **EEOFFSET**. On a write, this field contains the data to be stored at the word pointed to by **EEOFFSET**. For writes, configuring this field starts the write process. If protection and access rules do not permit reads, all 1s are returned. If protection and access rules do not permit writes, the write fails and the **EEDONE** register indicates failure.

Register 17: EEPROM Read-Write with Increment (EERDWRINC), offset 0x014

The **EERDWRINC** register is used to read or write the EEPROM word at the address pointed to by the **EEBLOCK** and **EEOFFSET** registers, and then increment the OFFSET field in the **EEOFFSET** register. If the protection or access rules do not permit access, the operation is handled as follows: if reading is not allowed, the value 0xFFF.FFFF is returned in all cases; if writing is not allowed, the **EEDONE** register is configured to indicate an error. In all cases, the OFFSET field is incremented. If the last value is reached, OFFSET wraps around to 0 and points to the first word.

EEPROM Read-Write with Increment (EERDWRINC)

Base 0x400A.F000 Offset 0x014 Type R/W, reset -



31:0 VALUE R/W - EEPROM Read or Write Data with Increment

On a read, this field contains the value at the word pointed to by **EEOFFSET**. On a write, this field contains the data to be stored at the word pointed to by **EEOFFSET**. For writes, configuring this field starts the write process. If protection and access rules do not permit reads, all 1s are returned. If protection and access rules do not permit writes, the write fails and the **EEDONE** register indicates failure.

Regardless of error, the OFFSET field in the **EEOFFSET** register is incremented by 1, and the value wraps around if the last word is reached.

Register 18: EEPROM Done Status (EEDONE), offset 0x018

The **EEDONE** register indicates the successful or failed completion of a write using the **EERDWR** or **EERDWRINC** register, protection set using the **EEPROT** register, password registered using the **EEPASS** register, copy buffer erase or program retry using the **EESUPP** register, or a debug mass erase using the **EEDBGME** register. The **EEDONE** register can be used with the **EEINT** register to generate an interrupt to report the status. The normal usage is to poll the **EEDONE** register or read the register after an interrupt is triggered. When the **EEDONE** bit 0 is set, then the operation is still in progress. When the **EEDONE** bit 0 is clear, then the value of **EEDONE** indicates the completion status. If **EEDONE**==0, then the write completed successfully. If **EEDONE**!=0, then an error occurred and the source of the error is given by the set bit(s). If an error occurs, corrective action may be taken as explained on page 564.

EEPROM Done Status (EEDONE)

Base 0x400A.F000 Offset 0x018


5

WRBUSY

RO

0

Type RO, reset 0x0000.0000



Bit/Field	Name	Type	Reset	Description
31:9	reserved	RO	0x0000.0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
8	INVPL	RO	0	Invalid Program Voltage Level
				Value Description
				0 No error
				An error occurred during programming due to the voltage level dropping below the level required for EEPROM programming. This operation can be retried, however the voltage must be stabilized before retrying.
7:6	reserved	RO	0x0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.

Value Description

0 No error

Write Busy

1 An attempt to access the EEPROM was made while a write was in progress.

Bit/Field	Name	Туре	Reset	Description
4	NOPERM	RO	0	Write Without Permission
				Value Description
				0 No error
				An attempt was made to write without permission. This error can result because the block is locked, the write violates the programmed access protection, or when an attempt is made to write a password when the password has already been written.
3	WKCOPY	RO	0	Working on a Copy
				Value Description
				0 The EEPROM is not copying.
				A write is in progress and is waiting for the EEPROM to copy to or from the copy buffer.
2	WKERASE	RO	0	Working on an Erase
				Value Description
				0 The EEPROM is not erasing.
				A write is in progress and the original block is being erased after being copied.
1	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
0	WORKING	RO	0	EEPROM Working
				Value Description
				0 The EEPROM is not working.
				1 The EEPROM is performing the requested operation.

February 20, 2013 563

Register 19: EEPROM Support Control and Status (EESUPP), offset 0x01C


The **EESUPP** register indicates if internal operations are required because an internal copy buffer must be erased or a programming failure has occurred and the operation must be completed. These conditions are explained below as well as in more detail in the section called "Manual Copy Buffer Erase" on page 535 and the section called "Error During Programming" on page 535.

- The EREQ bit is set if the internal copy buffer must be erased the next time it is used because it is full. To avoid the delay of waiting for the copy buffer to be erased on the next write, it can be erased manually using this register by setting the START bit.
- If either PRETRY or ERETRY is set indicating that an operation must be completed, setting the START bit causes the operation to be performed again.

These bits are not changed by reset, so any condition that occurred before a reset is still indicated after a reset.

EEPROM Support Control and Status (EESUPP)

Base 0x400A.F000 Offset 0x01C Type R/W, reset -



Bit/Field	Name	Type	Reset	Description
31:4	reserved	RO	0x0000.000	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
3	PRETRY	RO	-	Programming Must Be Retried
				Value Description
				0 Programming has not failed.
				1 Programming from a copy in either direction failed to complete and must be restarted by setting the START bit.
2	ERETRY	RO	-	Erase Must Be Retried

Value Description

- 0 Erasing has not failed.
- Erasing failed to complete and must be restarted by setting the START bit. If the failed erase is due to the erase of a main buffer, the copy will be performed after the erase completes successfully.

Bit/Field	Name	Type	Reset	Description
1	EREQ	RO	-	Erase Required
				Value Description The copy buffer has available space. An erase of the copy buffer is required.
0	START	R/W	0	Start Erase

Setting this bit starts error recovery if the PRETRY or ERETRY bit is set. If both the PRETRY and the ERETRY bits are clear, setting this bit starts erasing the copy buffer if EREQ is set. If none of the other bits in this register are set, setting this bit is ignored. After this bit is set, the WORKING bit in the **EEDONE** register is set and is cleared when the operation is complete. In addition, the **EEINT** register can be used to generate an interrupt on completion.

If this bit is set while an operation is in progress, the write is ignored. The ${\tt START}$ bit is automatically cleared when the operation completes.

February 20, 2013 565

Register 20: EEPROM Unlock (EEUNLOCK), offset 0x020

The **EEUNLOCK** register can be used to unlock the whole EEPROM or a single block using a password. Unlocking is only required if a password is registered using the **EEPASSn** registers for the block that is selected by the **EEBLOCK** register. If block 0 has a password, it locks the remaining blocks from any type of access, but uses its own protection mechanism, for example readable, but not writable when locked. In addition, if block 0 has a password, it must be unlocked before unlocking any other block.


The **EEUNLOCK** register is written between 1 and 3 times to form the 32-bit, 64-bit, or 96-bit password registered using the **EEPASSn** registers. The value used to configure the **EEPASS0** register must always be written last. For example, for a 96-bit password, the value used to configure the **EEPASS2** register must be written first followed by the **EEPASS1** and **EEPASS0** register values. The block or the whole EEPROM can be re-locked by writing 0xFFFF.FFFF to this register.

In the event that an invalid value is written to this register, the block remains locked. The state of the EEPROM lock can be determined by reading back the **EEUNLOCK** register. If a multi-word password is set and the number of words written is incorrect, writing 0xFFFF.FFFF to this register reverts the EEPROM lock to the locked state, and the proper unlock sequence can be retried.

Note that the internal logic is balanced to prevent any electrical or time-based attack being used to find the correct password or its length.

EEPROM Unlock (EEUNLOCK)

Base 0x400A.F000 Offset 0x020 Type R/W, reset -



Bit/Field Name Type Reset Description

31:0 UNLOCK R/W - EEPROM Unlock

Value Description

- 0 The EEPROM is locked.
- 1 The EEPROM is unlocked.


The EEPROM is locked if the block referenced by the **EEBLOCK** register has a password registered, or if the master block (block 0) has a password. Unlocking is performed by writing the password to this register. The block or the EEPROM stays unlocked until it is locked again or until the next reset. It can be locked again by writing 0xFFFF.FFFF to this register.

Register 21: EEPROM Protection (EEPROT), offset 0x030

The **EEPROT** register is used to set or read the protection for the current block, as selected by the **EEBLOCK** register. Protection and access control is used to determine when a block's contents can be read or written. The protection level for block 0 sets the minimum protection level for the entire EEPROM. For example, if the PROT field is configured to 0x1 for block 0, then block 1 could be configured with the PROT field to be 0x1, 0x2, or 0x3, but not 0x0.

EEPROM Protection (EEPROT)

Base 0x400A.F000 Offset 0x030 Type R/W, reset 0x0000.0000



Bit/Field	Name	Type	Reset	Description
31:4	reserved	RO	0x0000.000	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
3	ACC	R/W	0	Access Control

Value Description

- 0 Both user and supervisor code may access this block of the EEPROM.
- Only supervisor code may access this block of the EEPROM. μDMA and Debug are also prevented from accessing the EEPROM.

If this bit is set for block 0, then the whole EEPROM may only be accessed by supervisor code.

Bit/Field	Name	Туре	Reset	Description
2:0	PROT	R/W	0x0	Protection Control The Protection bits control what context is needed for reading and writing the block selected by the EEBLOCK register, or if block 0 is selected, all blocks. The following values are allowed:
				Value Description 0x0 This setting is the default. If there is no password, the block is
				not protected and is readable and writable. If there is a password, the block is readable, but only writable when unlocked.
				0x1 If there is a password, the block is readable or writable only when unlocked.
				This value has no meaning when there is no password.
				0x2 If there is no password, the block is readable, not writable.
				If there is a password, the block is readable only when unlocked, but is not writable under any conditions.
				0x3 Reserved

Register 22: EEPROM Password (EEPASS0), offset 0x034

Register 23: EEPROM Password (EEPASS1), offset 0x038


Register 24: EEPROM Password (EEPASS2), offset 0x03C

The **EEPASSn** registers are used to configure a password for a block. A password may only be set once and cannot be changed. The password may be 32-bits, 64-bits, or 96-bits. Each word of the password can be any 32-bit value other than 0xFFFF.FFFF (all 1s). To set a password, the **EEPASS0** register is written to with a value other than 0xFFFF.FFF. When the write completes, as indicated in the **EEDONE** register, the application may choose to write to the **EEPASS1** register with a value other than 0xFFFF.FFF. When that write completes, the application may choose to write to the EEPASS2 register with a value other than 0xFFFF.FFFF to create a 96-bit password. The registers do not have to be written consecutively, and the **EEPASS1** and **EEPASS2** registers may be written at a later date. Based on whether 1, 2, or all 3 registers have been written, the unlock code also requires the same number of words to unlock.

Once the password is written, the block is not actually locked until either a reset occurs or 0xFFFF.FFFF is written to **EEUNLOCK**.

EEPROM Password (EEPASSn)

Base 0x400A.F000 Offset 0x034 Type R/W, reset -



Bit/Field	Name	Type	Reset	Description
31:0	PASS	R/W	-	Password


This register reads as 0x1 if a password is registered for this block and 0x0 if no password is registered. A write to this register if it reads as 0x0 sets the password. If an attempt is made to write to this register when it reads as 0x1, the write is ignored and the NOPERM bit in the **EEDONE** register is set.

Register 25: EEPROM Interrupt (EEINT), offset 0x040

The **EEINT** register is used to control whether an interrupt should be generated when a write to EEPROM completes as indicated by the **EEDONE** register value changing from 0x1 to any other value. If the INT bit in this register is set, the ERIS bit in the **Flash Controller Raw Interrupt Status (FCRIS)** register is set whenever the **EEDONE** register value changes from 0x1 as the Flash memory and the EEPROM share an interrupt vector.

EEPROM Interrupt (EEINT)

Base 0x400A.F000 Offset 0x040 Type R/W, reset 0x0000.0000



Bit/Field	Name	Type	Reset	Description
31:1	reserved	RO	0x0000.000	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
0	INT	R/W	0	Interrupt Enable

Value Description

- 0 No interrupt is generated.
- An interrupt is generated when the **EEDONE** register transitions from 1 to 0 or an error occurs. The **EEDONE** register provides status after a write to an offset location as well as a write to the password and protection bits.

Register 26: EEPROM Block Hide (EEHIDE), offset 0x050


The **EEHIDE** register is used to hide one or more blocks other than block 0. Once hidden, the block is not accessible until the next reset. This model allows initialization code to have access to data which is not visible to the rest of the application. This register also provides for additional security in that there is no password to search for in the code or data.

EEPROM Block Hide (EEHIDE)

Base 0x400A.F000

31:1

Offset 0x050 Type R/W, reset 0x0000.0000



Value Description

Hide Block

- 0 The corresponding block is not hidden.
- 1 The block number that corresponds to the bit number is hidden. A hidden block cannot be accessed, and the OFFSET value in the **EEBLOCK** register cannot be set to that block number. If an attempt is made to configure the OFFSET field to a hidden block, the **EEBLOCK** register is cleared.

Any attempt to clear a bit in this register that is set is ignored.

0 RO reserved 0

Hn

R/W

0x0000.000

Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.

Register 27: EEPROM Debug Mass Erase (EEDBGME), offset 0x080

The **EEDBGME** register is used to mass erase the EEPROM block back to its default state from the factory. This register is intended to be used only for debug and test purposes, not in production environments. The erase takes place in such a way as to be secure. It first erases all data and then erases the protection mechanism. This register can only be written from supervisor mode by the core, and can also be written by the Stellaris debug controller when enabled. A key is used to avoid accidental use of this mechanism. Note that if a power down takes place while erasing, the mechanism should be used again to complete the operation. Powering off prematurely does not expose secured data.

To start a mass erase, the whole register must be written as 0xE37B.0001. The register reads back as 0x1 until the erase is fully completed at which time it reads as 0x0. The **EEDONE** register is set to 0x1 when the erase is started and changes to 0x0 or an error when the mass erase is complete.

Note that mass erasing the EEPROM block means that the wear-leveling counters are also reset to the factory default.

EEPROM Debug Mass Erase (EEDBGME)

Base 0x400A.F000

Offset 0x080

Type R/W, reset 0x0000.0000

_	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16
		ı	ı	ı		1		KE	Υ				1		ı	'
Type Reset	WO 0	WO 0	WO 0	WO 0	WO 0	WO 0	WO 0	WO 0	WO 0							
	15	14	13	12	11	10	9	8	7	6	5	4	3	2	1	0
		'	•	'	' !	'		reserved							•	ME
Type Reset	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	R/W 0							

Bit/Field	Name	Туре	Reset	Description
31:16	KEY	WO	0x0000	Erase Key This field must be written with 0xE37B for the ${\tt ME}$ field to be effective.
15:1	reserved	RO	0x000	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
0	ME	R/W	0	Mass Erase

Value Description


- No action.
- When written as a 1, the EEPROM is mass erased. This bit continues to read as 1 until the EEPROM is fully erased.


Register 28: EEPROM Peripheral Properties (EEPROMPP), offset 0xFC0

The **EEPROMPP** register indicates the size of the EEPROM for this part.

EEPROM Peripheral Properties (EEPROMPP)

Base 0x400A.F000 Offset 0xFC0





31:5	reserved	RO	0x0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
4:0	SIZE	RO	0x1F	2-KB EEPROM Size

8.6 **Memory Register Descriptions (System Control Offset)**

The remainder of this section lists and describes the registers that reside in the System Control address space, in numerical order by address offset. Registers in this section are relative to the System Control base address of 0x400F.E000.

Register 29: ROM Control (RMCTL), offset 0x0F0


This register provides control of the ROM controller state. This register offset is relative to the System Control base address of 0x400F.E000.

At reset, the following sequence is performed:

- 1. The **BOOTCFG** register is read. If the EN bit is clear, the ROM Boot Loader is executed.
- 2. In the ROM Boot Loader, the status of the specified GPIO pin is compared with the specified polarity. If the status matches the specified polarity, the ROM is mapped to address 0x0000.0000 and execution continues out of the ROM Boot Loader.
- 3. If the EN bit is set or the status doesn't match the specified polarity, the data at address 0x0000.0004 is read, and if the data at this address is 0xFFF.FFFF, the ROM is mapped to address 0x0000.0000 and execution continues out of the ROM Boot Loader.
- **4.** If there is data at address 0x0000.0004 that is not 0xFFF.FFFF, the stack pointer (**SP**) is loaded from Flash memory at address 0x0000.0000 and the program counter (**PC**) is loaded from address 0x0000.0004. The user application begins executing.

ROM Control (RMCTL)

Base 0x400F.E000 Offset 0x0F0 Type R/W1C, reset -



Bit/Field	Name	Туре	Reset	Description
31:1	reserved	RO	0x0000.000	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
0	ВА	R/W1C	1	Boot Alias

Value Description

- 0 The Flash memory is at address 0x0.
- 1 The microcontroller's ROM appears at address 0x0.

This bit is cleared by writing a 1 to this bit position.

Register 30: Flash Memory Protection Read Enable 0 (FMPRE0), offset 0x130 and 0x200

Register 31: Flash Memory Protection Read Enable 1 (FMPRE1), offset 0x204 Register 32: Flash Memory Protection Read Enable 2 (FMPRE2), offset 0x208 Register 33: Flash Memory Protection Read Enable 3 (FMPRE3), offset 0x20C

Note: The **FMPRE0** register is aliased for backwards compatibility.

Note: Offset is relative to System Control base address of 0x400F.E000.

This register stores the read-only protection bits for each 2-KB flash block (**FMPPEn** stores the execute-only bits).

This register is loaded during the power-on reset sequence. The factory settings for the **FMPREn** and **FMPPEn** registers are a value of 1 for all implemented 2-KB blocks. This achieves a policy of open access and programmability. The register bits may be changed by writing the specific register bit. However, this register is R/W0; the user can only change the protection bit from a 1 to a 0 (and may NOT change a 0 to a 1). The changes are not permanent until the register is committed (saved), at which point the bit change is permanent. If a bit is changed from a 1 to a 0 and not committed, it may be restored by executing a power-on reset sequence. The reset value shown only applies to power-on reset; any other type of reset does not affect this register. Once committed, the only way to restore the factory default value of this register is to perform the sequence detailed in "Recovering a "Locked" Microcontroller" on page 209.

Each **FMPREn** register controls a 64-k block of Flash. For additional information, see "Flash Memory Protection" on page 526.

FMPRE0: 0 to 64 KB
 FMPRE1: 65 to 128 KB
 FMPRE2: 129 to 192 KB
 FMPRE3: 193 to 256 KB


Flash Memory Protection Read Enable n (FMPREn)

READ_ENABLE

R/W

Base 0x400F.E000 Offset 0x130 and 0x200 Type R/W, reset 0xFFF.FFFF

31:0



0xFFFF.FFFF Flash Read Enable

Each bit configures a 2-KB flash block to be read only.

The policies may be combined as shown in Table 8-1 on page 527.

Register 34: Flash Memory Protection Program Enable 0 (FMPPE0), offset 0x134 and 0x400

Register 35: Flash Memory Protection Program Enable 1 (FMPPE1), offset 0x404

Register 36: Flash Memory Protection Program Enable 2 (FMPPE2), offset 0x408

Register 37: Flash Memory Protection Program Enable 3 (FMPPE3), offset 0x40C

Note: The FMPPE0 register is aliased for backwards compatibility.

Note: Offset is relative to System Control base address of 0x400FE000.

This register stores the execute-only protection bits for each 2-KB flash block (**FMPREn** stores the read-only protection bits).


This register is loaded during the power-on reset sequence. The factory settings for the **FMPREn** and **FMPPEn** registers are a value of 1 for all implemented banks. This achieves a policy of open access and programmability. The register bits may be changed by writing the specific register bit. However, this register is R/W0; the user can only change the protection bit from a 1 to a 0 (and may NOT change a 0 to a 1). The changes are not permanent until the register is committed (saved), at which point the bit change is permanent. If a bit is changed from a 1 to a 0 and not committed, it may be restored by executing a power-on reset sequence. The reset value shown only applies to power-on reset; any other type of reset does not affect this register. Once committed, the only way to restore the factory default value of this register is to perform the sequence detailed in "Recovering a "Locked" Microcontroller" on page 209. For additional information, see "Flash Memory Protection" on page 526.

Each **FMPPEn** register controls a 64-k block of Flash. For additional information, see "Flash Memory Protection" on page 526.

FMPPE0: 0 to 64 KB
 FMPPE1: 65 to 128 KB
 FMPPE2: 129 to 192 KB
 FMPPE3: 193 to 256 KB

Flash Memory Protection Program Enable n (FMPPEn)

Base 0x400F.E000 Offset 0x134 and 0x400 Type R/W, reset 0xFFFF.FFFF



Bit/Field	Name	Туре	Reset	Description
31:0	PROG_ENABLE	R/W	0xFFFF.FFFF	Flash Programming Enable
				Each bit configures a 2-KB flash block to be execute only.
				The policies may be combined as shown in Table 8-1 on page 527.

February 20, 2013 577

Register 38: Boot Configuration (BOOTCFG), offset 0x1D0

Note: Offset is relative to System Control base address of 0x400F.E000.

Note: The **Boot Configuration (BOOTCFG)** register requires a POR before the committed changes take effect.

This register is not written directly, but instead uses the **FMD** register as explained in "Non-Volatile Register Programming" on page 530. This register provides configuration of a GPIO pin to enable the ROM Boot Loader as well as a write-once mechanism to disable external debugger access to the device. At reset, the user has the opportunity to direct the core to execute the ROM Boot Loader or the application in Flash memory by using any GPIO signal from Ports A-Q as configured by the bits in this register. At reset, the following sequence is performed:


- 1. The **BOOTCFG** register is read. If the EN bit is clear, the ROM Boot Loader is executed.
- 2. In the ROM Boot Loader, the status of the specified GPIO pin is compared with the specified polarity. If the status matches the specified polarity, the ROM is mapped to address 0x0000.0000 and execution continues out of the ROM Boot Loader.
- 3. If the EN bit is set or the status doesn't match the specified polarity, the data at address 0x0000.0004 is read, and if the data at this address is 0xFFFF.FFF, the ROM is mapped to address 0x0000.0000 and execution continues out of the ROM Boot Loader.
- **4.** If there is data at address 0x0000.0004 that is not 0xFFF.FFFF, the stack pointer (**SP**) is loaded from Flash memory at address 0x0000.0000 and the program counter (**PC**) is loaded from address 0x0000.0004. The user application begins executing.

The DBG0 bit is cleared by the factory and the DBG1 bit is set, which enables external debuggers. Clearing the DBG1 bit disables any external debugger access to the device, starting with the next power-up cycle of the device. The NW bit indicates that bits in the register can be changed from 1 to 0. Software can clear the NW bit to prevent further changes to the bits in this register.

By committing the register values using the COMT bit in the **FMC** register, the register contents become non-volatile and are therefore retained following power cycling. Prior to being committed, bits can only be changed from 1 to 0. The reset value shown only applies to power-on reset when the register is not yet committed; any other type of reset does not affect this register. Once committed, the register retains its value through power-on reset. Once committed, the only way to restore the factory default value of this register is to perform the sequence detailed in "Recovering a "Locked" Microcontroller" on page 209.

Boot Configuration (BOOTCFG)

Base 0x400F.E000 Offset 0x1D0 Type RO, reset 0xFFFF.FFFE



Bit/Field	Name	Туре	Reset	Description
31	NW	RO	1	Not Written When set, this bit indicates that the values in this register can be changed from 1 to 0. When clear, this bit specifies that the contents of this register cannot be changed.
30:16	reserved	RO	0xFFFF	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
15:13	PORT	RO	0x7	Boot GPIO Port This field selects the port of the GPIO port pin that enables the ROM boot loader at reset.
				Value Description 0x0 Port A 0x1 Port B 0x2 Port C 0x3 Port D 0x4 Port E 0x5 Port F 0x6 Port G 0x7 Port H
12:10	PIN	RO	0×7	Boot GPIO Pin This field selects the pin number of the GPIO port pin that enables the ROM boot loader at reset. Value Description 0x0 Pin 0 0x1 Pin 1 0x2 Pin 2 0x3 Pin 3 0x4 Pin 4 0x5 Pin 5 0x6 Pin 6 0x7 Pin 7
9	POL	RO	1	Boot GPIO Polarity When set, this bit selects a high level for the GPIO port pin to enable the ROM boot loader at reset. When clear, this bit selects a low level for the GPIO port pin.
8	EN	RO	1	Boot GPIO Enable Clearing this bit enables the use of a GPIO pin to enable the ROM Boot Loader at reset. When this bit is set, the contents of address 0x0000.0004 are checked to see if the Flash memory has been programmed. If the contents are not 0xFFFF.FFFF, the core executes out of Flash memory. If the Flash has not been programmed, the core executes out of ROM.

Bit/Field	Name	Туре	Reset	Description
7:5	reserved	RO	0x7	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
4	KEY	RO	1	 KEY Select This bit chooses between using the value 0xA442 or 0x71D5 as the WRKEY value in the FMC/FMC2 register. Value Description The value 0x71D5 is used as the WRKEY in the FMC/FMC2 register. Writes to the FMC/FMC2 register with a 0xA442 key are ignored. 0xA442 is used as the WRKEY in the FMC/FMC2 register. Writes to the FMC/FMC2 register with a 0x71D5 key are ignored.
3:2	reserved	RO	0x3	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
1	DBG1	RO	1	Debug Control 1 The DBG1 bit must be 1 and DBG0 must be 0 for debug to be available.
0	DBG0	RO	0	Debug Control 0 The DBG1 bit must be 1 and DBG0 must be 0 for debug to be available.

Register 39: User Register 0 (USER REG0), offset 0x1E0

Register 40: User Register 1 (USER_REG1), offset 0x1E4

Register 41: User Register 2 (USER_REG2), offset 0x1E8

Register 42: User Register 3 (USER_REG3), offset 0x1EC


Note: Offset is relative to System Control base address of 0x400F.E000.

These registers each provide 32 bits of user-defined data that is non-volatile. Bits can only be changed from 1 to 0. The reset value shown only applies to power-on reset when the register is not yet committed; any other type of reset does not affect this register. Once committed, the register retains its value through power-on reset. Once committed, the only way to restore the factory default value of this register is to perform the sequence detailed in "Recovering a "Locked" Microcontroller" on page 209.

User Register n (USER_REGn)

Base 0x400F.E000 Offset 0x1E0

Type R/W, reset 0xFFF.FFF



Contains the user data value. This field is initialized to all 1s and once committed, retains its value through power-on reset.

9 Micro Direct Memory Access (µDMA)


The LM4F232H5QC microcontroller includes a Direct Memory Access (DMA) controller, known as micro-DMA (μ DMA). The μ DMA controller provides a way to offload data transfer tasks from the Cortex TM-M4F processor, allowing for more efficient use of the processor and the available bus bandwidth. The μ DMA controller can perform transfers between memory and peripherals. It has dedicated channels for each supported on-chip module and can be programmed to automatically perform transfers between peripherals and memory as the peripheral is ready to transfer more data. The μ DMA controller provides the following features:

- ARM[®] PrimeCell[®] 32-channel configurable µDMA controller
- Support for memory-to-memory, memory-to-peripheral, and peripheral-to-memory in multiple transfer modes
 - Basic for simple transfer scenarios
 - Ping-pong for continuous data flow
 - Scatter-gather for a programmable list of up to 256 arbitrary transfers initiated from a single request
- Highly flexible and configurable channel operation
 - Independently configured and operated channels
 - Dedicated channels for supported on-chip modules
 - Flexible channel assignments
 - One channel each for receive and transmit path for bidirectional modules
 - Dedicated channel for software-initiated transfers
 - Per-channel configurable priority scheme
 - Optional software-initiated requests for any channel
- Two levels of priority
- Design optimizations for improved bus access performance between µDMA controller and the processor core
 - µDMA controller access is subordinate to core access
 - RAM striping
 - Peripheral bus segmentation
- Data sizes of 8, 16, and 32 bits
- Transfer size is programmable in binary steps from 1 to 1024
- Source and destination address increment size of byte, half-word, word, or no increment

- Maskable peripheral requests
- Interrupt on transfer completion, with a separate interrupt per channel

9.1 Block Diagram

Figure 9-1. µDMA Block Diagram



9.2 Functional Description

The μ DMA controller is a flexible and highly configurable DMA controller designed to work efficiently with the microcontroller's Cortex-M4F processor core. It supports multiple data sizes and address increment schemes, multiple levels of priority among DMA channels, and several transfer modes to allow for sophisticated programmed data transfers. The μ DMA controller's usage of the bus is always subordinate to the processor core, so it never holds up a bus transaction by the processor. Because the μ DMA controller is only using otherwise-idle bus cycles, the data transfer bandwidth it provides is essentially free, with no impact on the rest of the system. The bus architecture has been optimized to greatly enhance the ability of the processor core and the μ DMA controller to efficiently share the on-chip bus, thus improving performance. The optimizations include RAM striping and peripheral bus segmentation, which in many cases allow both the processor core and the μ DMA controller to access the bus and perform simultaneous data transfers.

The μ DMA controller can transfer data to and from the on-chip SRAM. However, because the Flash memory and ROM are located on a separate internal bus, it is not possible to transfer data from the Flash memory or ROM with the μ DMA controller.

Each peripheral function that is supported has a dedicated channel on the μDMA controller that can be configured independently. The μDMA controller implements a unique configuration method using channel control structures that are maintained in system memory by the processor. While simple transfer modes are supported, it is also possible to build up sophisticated "task" lists in memory that allow the μDMA controller to perform arbitrary-sized transfers to and from arbitrary locations as part of a single transfer request. The μDMA controller also supports the use of ping-pong buffering to accommodate constant streaming of data to or from a peripheral.

Each channel also has a configurable arbitration size. The arbitration size is the number of items that are transferred in a burst before the μDMA controller rearbitrates for channel priority. Using the arbitration size, it is possible to control exactly how many items are transferred to or from a peripheral each time it makes a μDMA service request.

9.2.1 Channel Assignments

Each DMA channel has up to five possible assignments which are selected using the **DMA Channel Map Select n (DMACHMAPn)** registers with 4-bit assignment fields for each µDMA channel.

Table 9-1 on page 584 shows the µDMA channel mapping. The Enc. column shows the encoding for the respective **DMACHMAPn** bit field. Encodings 0x5 - 0xF are all reserved. To support legacy software which uses the **DMA Channel Assignment (DMACHASGN)** register, Enc. 0 is equivalent to a **DMACHASGN** bit being clear, and Enc. 1 is equivalent to a **DMACHASGN** bit being set. If the **DMACHASGN** register is read, bit fields return 0 if the corresponding **DMACHMAPn** register field value are equal to 0, otherwise they return 1 if the corresponding **DMACHMAPn** register field values are not equal to 0. The Type indication in the table indicates if a particular peripheral uses a single request (S), burst request (B) or either (SB).

Note: Channels noted in the table as "Software" may be assigned to peripherals in the future. However, they are currently available for software use. Channel 30 is dedicated for software use.

The USB endpoints mapped to μ DMA channels 0-3 can be changed with the **USBDMASEL** register (see page 1216).

Table 9-1. µDMA Channel Assignments

Enc.	nc. 0		1		2	3		4		
Ch#	Peripheral	Туре	Peripheral	Туре	Peripheral	Туре	Peripheral	Туре	Peripheral	Туре
0	USB0 EP1 RX	SB	UART2 RX	SB	Software	В	GPTimer 4A	В	Software	В
1	USB0 EP1 TX	В	UART2 TX	SB	Software	В	GPTimer 4B	В	Software	В
2	USB0 EP2 RX	В	GPTimer 3A	В	Software	В	Software	В	Software	В
3	USB0 EP2 TX	В	GPTimer 3B	В	Software	В	Software	В	Software	В
4	USB0 EP3 RX	В	GPTimer 2A	В	Software	В	GPIO A	В	Software	В
5	USB0 EP3 TX	В	GPTimer 2B	В	Software	В	GPIO B	В	Software	В
6	Software	В	GPTimer 2A	В	UART5 RX	SB	GPIO C	В	Software	В
7	Software	В	GPTimer 2B	В	UART5 TX	SB	GPIO D	В	Software	В
8	UART0 RX	SB	UART1 RX	SB	Software	В	GPTimer 5A	В	Software	В
9	UART0 TX	SB	UART1 TX	SB	Software	В	GPTimer 5B	В	Software	В
10	SSI0 RX	SB	SSI1 RX	SB	UART6 RX	SB	GPTimer 6A	В	Software	В
11	SSI0 TX	SB	SSI1 TX	SB	UART6 TX	SB	GPTimer 6B	В	Software	В
12	Software	В	UART2 RX	SB	SSI2 RX	SB	GPTimer 7A	В	GPIO K	В
13	Software	В	UART2 TX	SB	SSI2 TX	SB	GPTimer 7B	В	Software	В
14	ADC0 SS0	В	GPTimer 2A	В	SSI3 RX	SB	GPIO E	В	Software	В
15	ADC0 SS1	В	GPTimer 2B	В	SSI3 TX	SB	GPIO F	В	Software	В
16	ADC0 SS2	В	Software	В	UART3 RX	SB	GPTimer 8A	В	Software	В
17	ADC0 SS3	В	Software	В	UART3 TX	SB	GPTimer 8B	В	Software	В
18	GPTimer 0A	В	GPTimer 1A	В	UART4 RX	SB	GPIO B	В	Software	В
19	GPTimer 0B	В	GPTimer 1B	В	UART4 TX	SB	GPIO G	В	Software	В
20	GPTimer 1A	В	Software	В	UART7 RX	SB	GPIO H	В	Software	В

Enc. 2 3 4 Ch# Peripheral **Peripheral Peripheral** Type Peripheral Type Type Peripheral Type Type **GPTimer 1B** В Software В **UART7 TX** SB **GPIO J** В Software В 21 UART1 RX 22 SB Software В Software В Software В Software В **UART1 TX** SB 23 Software В Software В Software В Software В SSI1 RX SB ADC1 SS0 В Software В **GPTimer 9A** В Software В 24 SSI1 TX ADC1 SS1 GPTimer 9B Software В 25 SB В Software В В ADC1 SS2 **GPTimer 10A** 26 Software В В Software В В Software В ADC1 SS3 27 Software В В Software В **GPTimer 10B** В Software В **GPTimer 11A** 28 Software В Software В Software В В Software В Software В Software Software **GPTimer 11B** В Software 29 B В В

Table 9-1. µDMA Channel Assignments (continued)

В

В

Software

Reserved

В

В

Software

Reserved

9.2.2 Priority

Software

Reserved

30

31

The µDMA controller assigns priority to each channel based on the channel number and the priority level bit for the channel. Channel number 0 has the highest priority and as the channel number increases, the priority of a channel decreases. Each channel has a priority level bit to provide two levels of priority: default priority and high priority. If the priority level bit is set, then that channel has higher priority than all other channels at default priority. If multiple channels are set for high priority, then the channel number is used to determine relative priority among all the high priority channels.

В

В

Software

Reserved

В

В

Software

Reserved

В

В

The priority bit for a channel can be set using the **DMA Channel Priority Set (DMAPRIOSET)** register and cleared with the **DMA Channel Priority Clear (DMAPRIOCLR)** register.

9.2.3 Arbitration Size

When a μ DMA channel requests a transfer, the μ DMA controller arbitrates among all the channels making a request and services the μ DMA channel with the highest priority. Once a transfer begins, it continues for a selectable number of transfers before rearbitrating among the requesting channels again. The arbitration size can be configured for each channel, ranging from 1 to 1024 item transfers. After the μ DMA controller transfers the number of items specified by the arbitration size, it then checks among all the channels making a request and services the channel with the highest priority.

If a lower priority μ DMA channel uses a large arbitration size, the latency for higher priority channels is increased because the μ DMA controller completes the lower priority burst before checking for higher priority requests. Therefore, lower priority channels should not use a large arbitration size for best response on high priority channels.

The arbitration size can also be thought of as a burst size. It is the maximum number of items that are transferred at any one time in a burst. Here, the term arbitration refers to determination of μDMA channel priority, not arbitration for the bus. When the μDMA controller arbitrates for the bus, the processor always takes priority. Furthermore, the μDMA controller is held off whenever the processor must perform a bus transaction on the same bus, even in the middle of a burst transfer.

9.2.4 Request Types

The μ DMA controller responds to two types of requests from a peripheral: single or burst. Each peripheral may support either or both types of requests. A single request means that the peripheral

is ready to transfer one item, while a burst request means that the peripheral is ready to transfer multiple items.

The μ DMA controller responds differently depending on whether the peripheral is making a single request or a burst request. If both are asserted, and the μ DMA channel has been set up for a burst transfer, then the burst request takes precedence. See Table 9-2 on page 586, which shows how each peripheral supports the two request types.

Table 9-2. Request Type Support

Peripheral	Event that generates Single Request	Event that generates Burst Request
ADC	None	FIFO half full
General-Purpose Timer	None	Trigger event
GPIO	Raw interrupt pulse	None
SSI TX	TX FIFO Not Full	TX FIFO Level (fixed at 4)
SSI RX	RX FIFO Not Empty	RX FIFO Level (fixed at 4)
UART TX	TX FIFO Not Full	TX FIFO Level (configurable)
UART RX	RX FIFO Not Empty	RX FIFO Level (configurable)
USB TX	None	FIFO TXRDY
USB RX	None	FIFO RXRDY

9.2.4.1 Single Request

When a single request is detected, and not a burst request, the µDMA controller transfers one item and then stops to wait for another request.

9.2.4.2 Burst Request

When a burst request is detected, the μ DMA controller transfers the number of items that is the lesser of the arbitration size or the number of items remaining in the transfer. Therefore, the arbitration size should be the same as the number of data items that the peripheral can accommodate when making a burst request. For example, the UART generates a burst request based on the FIFO trigger level. In this case, the arbitration size should be set to the amount of data that the FIFO can transfer when the trigger level is reached. A burst transfer runs to completion once it is started, and cannot be interrupted, even by a higher priority channel. Burst transfers complete in a shorter time than the same number of non-burst transfers.

It may be desirable to use only burst transfers and not allow single transfers. For example, perhaps the nature of the data is such that it only makes sense when transferred together as a single unit rather than one piece at a time. The single request can be disabled by using the **DMA Channel Useburst Set (DMAUSEBURSTSET)** register. By setting the bit for a channel in this register, the µDMA controller only responds to burst requests for that channel.

9.2.5 Channel Configuration

The μ DMA controller uses an area of system memory to store a set of channel control structures in a table. The control table may have one or two entries for each μ DMA channel. Each entry in the table structure contains source and destination pointers, transfer size, and transfer mode. The control table can be located anywhere in system memory, but it must be contiguous and aligned on a 1024-byte boundary.

Table 9-3 on page 587 shows the layout in memory of the channel control table. Each channel may have one or two control structures in the control table: a primary control structure and an optional alternate control structure. The table is organized so that all of the primary entries are in the first

half of the table, and all the alternate structures are in the second half of the table. The primary entry is used for simple transfer modes where transfers can be reconfigured and restarted after each transfer is complete. In this case, the alternate control structures are not used and therefore only the first half of the table must be allocated in memory; the second half of the control table is not necessary, and that memory can be used for something else. If a more complex transfer mode is used such as ping-pong or scatter-gather, then the alternate control structure is also used and memory space should be allocated for the entire table.

Any unused memory in the control table may be used by the application. This includes the control structures for any channels that are unused by the application as well as the unused control word for each channel.

Table 9-3. Control Structure Memory Map

Offset	Channel
0x0	0, Primary
0x10	1, Primary
0x1F0	31, Primary
0x200	0, Alternate
0x210	1, Alternate
0x3F0	31, Alternate

Table 9-4 shows an individual control structure entry in the control table. Each entry is aligned on a 16-byte boundary. The entry contains four long words: the source end pointer, the destination end pointer, the control word, and an unused entry. The end pointers point to the ending address of the transfer and are inclusive. If the source or destination is non-incrementing (as for a peripheral register), then the pointer should point to the transfer address.

Table 9-4. Channel Control Structure

Offset	Description
0x000	Source End Pointer
0x004	Destination End Pointer
0x008	Control Word
0x00C	Unused

The control word contains the following fields:

- Source and destination data sizes
- Source and destination address increment size
- Number of transfers before bus arbitration
- Total number of items to transfer
- Useburst flag
- Transfer mode

The control word and each field are described in detail in " μ DMA Channel Control Structure" on page 605. The μ DMA controller updates the transfer size and transfer mode fields as the transfer is performed. At the end of a transfer, the transfer size indicates 0, and the transfer mode indicates "stopped." Because the control word is modified by the μ DMA controller, it must be reconfigured before each new transfer. The source and destination end pointers are not modified, so they can be left unchanged if the source or destination addresses remain the same.

Prior to starting a transfer, a μ DMA channel must be enabled by setting the appropriate bit in the **DMA Channel Enable Set (DMAENASET)** register. A channel can be disabled by setting the channel bit in the **DMA Channel Enable Clear (DMAENACLR)** register. At the end of a complete μ DMA transfer, the controller automatically disables the channel.

9.2.6 Transfer Modes

The µDMA controller supports several transfer modes. Two of the modes support simple one-time transfers. Several complex modes support a continuous flow of data.

9.2.6.1 Stop Mode

While Stop is not actually a transfer mode, it is a valid value for the mode field of the control word. When the mode field has this value, the μ DMA controller does not perform any transfers and disables the channel if it is enabled. At the end of a transfer, the μ DMA controller updates the control word to set the mode to Stop.

9.2.6.2 Basic Mode

In Basic mode, the μ DMA controller performs transfers as long as there are more items to transfer, and a transfer request is present. This mode is used with peripherals that assert a μ DMA request signal whenever the peripheral is ready for a data transfer. Basic mode should not be used in any situation where the request is momentary even though the entire transfer should be completed. For example, a software-initiated transfer creates a momentary request, and in Basic mode, only the number of transfers specified by the ARBSIZE field in the **DMA Channel Control Word (DMACHCTL)** register is transferred on a software request, even if there is more data to transfer.

When all of the items have been transferred using Basic mode, the μDMA controller sets the mode for that channel to Stop.

9.2.6.3 Auto Mode

Auto mode is similar to Basic mode, except that once a transfer request is received, the transfer runs to completion, even if the µDMA request is removed. This mode is suitable for software-triggered transfers. Generally, Auto mode is not used with a peripheral.

When all the items have been transferred using Auto mode, the µDMA controller sets the mode for that channel to Stop.


9.2.6.4 **Ping-Pong**

Ping-Pong mode is used to support a continuous data flow to or from a peripheral. To use Ping-Pong mode, both the primary and alternate data structures must be implemented. Both structures are set up by the processor for data transfer between memory and a peripheral. The transfer is started using the primary control structure. When the transfer using the primary control structure is complete, the µDMA controller reads the alternate control structure for that channel to continue the transfer. Each time this happens, an interrupt is generated, and the processor can reload the control structure for the just-completed transfer. Data flow can continue indefinitely this way, using the primary and alternate control structures to switch back and forth between buffers as the data flows to or from the peripheral.

Refer to Figure 9-2 on page 589 for an example showing operation in Ping-Pong mode.

μDMA Controller **Cortex-M3 Processor** SOURCE DEST transfers using BUFFER A Primary Structure BUFFER A

Figure 9-2. Example of Ping-Pong µDMA Transaction



9.2.6.5 **Memory Scatter-Gather**

Memory Scatter-Gather mode is a complex mode used when data must be transferred to or from varied locations in memory instead of a set of contiguous locations in a memory buffer. For example, a gather µDMA operation could be used to selectively read the payload of several stored packets of a communication protocol and store them together in sequence in a memory buffer.

In Memory Scatter-Gather mode, the primary control structure is used to program the alternate control structure from a table in memory. The table is set up by the processor software and contains a list of control structures, each containing the source and destination end pointers, and the control word for a specific transfer. The mode of each control word must be set to Scatter-Gather mode. Each entry in the table is copied in turn to the alternate structure where it is then executed. The μ DMA controller alternates between using the primary control structure to copy the next transfer instruction from the list and then executing the new transfer instruction. The end of the list is marked by programming the control word for the last entry to use Auto transfer mode. Once the last transfer is performed using Auto mode, the μ DMA controller stops. A completion interrupt is generated only after the last transfer. It is possible to loop the list by having the last entry copy the primary control structure to point back to the beginning of the list (or to a new list). It is also possible to trigger a set of other channels to perform a transfer, either directly, by programming a write to the software trigger for another channel, or indirectly, by causing a peripheral action that results in a μ DMA request.

By programming the μ DMA controller using this method, a set of up to 256 arbitrary transfers can be performed based on a single μ DMA request.

Refer to Figure 9-3 on page 591 and Figure 9-4 on page 592, which show an example of operation in Memory Scatter-Gather mode. This example shows a *gather* operation, where data in three separate buffers in memory is copied together into one buffer. Figure 9-3 on page 591 shows how the application sets up a μ DMA task list in memory that is used by the controller to perform three sets of copy operations from different locations in memory. The primary control structure for the channel that is used for the operation is configured to copy from the task list to the alternate control structure.

Figure 9-4 on page 592 shows the sequence as the μDMA controller performs the three sets of copy operations. First, using the primary control structure, the μDMA controller loads the alternate control structure with task A. It then performs the copy operation specified by task A, copying the data from the source buffer A to the destination buffer. Next, the μDMA controller again uses the primary control structure to load task B into the alternate control structure, and then performs the B operation with the alternate control structure. The process is repeated for task C.





Figure 9-3. Memory Scatter-Gather, Setup and Configuration

NOTES:


- 1. Application has a need to copy data items from three separate locations in memory into one combined buffer.
- 2. Application sets up μDMA "task list" in memory, which contains the pointers and control configuration for three μDMA copy "tasks."
- 3. Application sets up the channel primary control structure to copy each task configuration, one at a time, to the alternate control structure, where it is executed by the μDMA controller.
- 4. The SRC and DST pointers in the task list must point to the last location in the corresponding buffer.

Figure 9-4. Memory Scatter-Gather, µDMA Copy Sequence




Using the channel's primary control structure, the μDMA controller copies task A configuration to the channel's alternate control structure.

Then, using the channel's alternate control structure, the μDMA controller copies data from the source buffer A to the destination buffer.



Using the channel's primary control structure, the μDMA controller copies task B configuration to the channel's alternate control structure.

Then, using the channel's alternate control structure, the μDMA controller copies data from the source buffer B to the destination buffer.



Using the channel's primary control structure, the μDMA controller copies task C configuration to the channel's alternate control structure.

Then, using the channel's alternate control structure, the μDMA controller copies data from the source buffer C to the destination buffer.

9.2.6.6 Peripheral Scatter-Gather

Peripheral Scatter-Gather mode is very similar to Memory Scatter-Gather, except that the transfers are controlled by a peripheral making a μ DMA request. Upon detecting a request from the peripheral, the μ DMA controller uses the primary control structure to copy one entry from the list to the alternate control structure and then performs the transfer. At the end of this transfer, the next transfer is started only if the peripheral again asserts a μ DMA request. The μ DMA controller continues to perform transfers from the list only when the peripheral is making a request, until the last transfer is complete. A completion interrupt is generated only after the last transfer.

By using this method, the μ DMA controller can transfer data to or from a peripheral from a set of arbitrary locations whenever the peripheral is ready to transfer data.

Refer to Figure 9-5 on page 594 and Figure 9-6 on page 595, which show an example of operation in Peripheral Scatter-Gather mode. This example shows a gather operation, where data from three separate buffers in memory is copied to a single peripheral data register. Figure 9-5 on page 594 shows how the application sets up a μ DMA task list in memory that is used by the controller to perform three sets of copy operations from different locations in memory. The primary control structure for the channel that is used for the operation is configured to copy from the task list to the alternate control structure.

Figure 9-6 on page 595 shows the sequence as the μ DMA controller performs the three sets of copy operations. First, using the primary control structure, the μ DMA controller loads the alternate control structure with task A. It then performs the copy operation specified by task A, copying the data from the source buffer A to the peripheral data register. Next, the μ DMA controller again uses the primary control structure to load task B into the alternate control structure, and then performs the B operation with the alternate control structure. The process is repeated for task C.





Figure 9-5. Peripheral Scatter-Gather, Setup and Configuration

NOTES:


- Application has a need to copy data items from three separate locations in memory into a peripheral data register.
- Application sets up μDMA "task list" in memory, which contains the pointers and control configuration for three μDMA copy "tasks."
- 3. Application sets up the channel primary control structure to copy each task configuration, one at a time, to the alternate control structure, where it is executed by the μDMA controller.

Figure 9-6. Peripheral Scatter-Gather, µDMA Copy Sequence



Using the channel's primary control structure, the μDMA controller copies task A configuration to the channel's alternate control structure.


Then, using the channel's alternate control structure, the μDMA controller copies data from the source buffer A to the peripheral data register.



Using the channel's primary control structure, the μDMA controller copies task B configuration to the channel's alternate control structure.

Then, using the channel's alternate control structure, the μDMA controller copies data from the source buffer B to the peripheral data register.

Task List μDMA Control Table Buffers in Memory in Memory



Using the channel's primary control structure, the μDMA controller copies task C configuration to the channel's alternate control structure.

Then, using the channel's alternate control structure, the μDMA controller copies data from the source buffer C to the peripheral data register.

9.2.7 Transfer Size and Increment

The μDMA controller supports transfer data sizes of 8, 16, or 32 bits. The source and destination data size must be the same for any given transfer. The source and destination address can be auto-incremented by bytes, half-words, or words, or can be set to no increment. The source and destination address increment values can be set independently, and it is not necessary for the address increment to match the data size as long as the increment is the same or larger than the data size. For example, it is possible to perform a transfer using 8-bit data size, but using an address increment of full words (4 bytes). The data to be transferred must be aligned in memory according to the data size (8, 16, or 32 bits).

Table 9-5 shows the configuration to read from a peripheral that supplies 8-bit data.

Table 9-5. µDMA Read Example: 8-Bit Peripheral

Field	Configuration
Source data size	8 bits
Destination data size	8 bits
Source address increment	No increment
Destination address increment	Byte
Source end pointer	Peripheral read FIFO register
Destination end pointer	End of the data buffer in memory

9.2.8 Peripheral Interface

Each peripheral that supports μ DMA has a single request and/or burst request signal that is asserted when the peripheral is ready to transfer data (see Table 9-2 on page 586). The request signal can be disabled or enabled using the **DMA Channel Request Mask Set (DMAREQMASKSET)** and **DMA Channel Request Mask Clear (DMAREQMASKCLR)** registers. The μ DMA request signal is disabled, or masked, when the channel request mask bit is set. When the request is not masked, the μ DMA channel is configured correctly and enabled, and the peripheral asserts the request signal, the μ DMA controller begins the transfer.

Note: When using μ DMA to transfer data to and from a peripheral, the peripheral must disable all interrupts to the NVIC.

When a μ DMA transfer is complete, the μ DMA controller generates an interrupt, see "Interrupts and Errors" on page 597 for more information.

For more information on how a specific peripheral interacts with the μ DMA controller, refer to the DMA Operation section in the chapter that discusses that peripheral.

9.2.9 Software Request

One μ DMA channel is dedicated to software-initiated transfers. This channel also has a dedicated interrupt to signal completion of a μ DMA transfer. A transfer is initiated by software by first configuring and enabling the transfer, and then issuing a software request using the **DMA Channel Software Request (DMASWREQ)** register. For software-based transfers, the Auto transfer mode should be used.

It is possible to initiate a transfer on any channel using the **DMASWREQ** register. If a request is initiated by software using a peripheral μ DMA channel, then the completion interrupt occurs on the interrupt vector for the peripheral instead of the software interrupt vector. Any channel may be used for software requests as long as the corresponding peripheral is not using μ DMA for data transfer.

9.2.10 Interrupts and Errors

When a μ DMA transfer is complete, the μ DMA controller generates a completion interrupt on the interrupt vector of the peripheral. Therefore, if μ DMA is used to transfer data for a peripheral and interrupts are used, then the interrupt handler for that peripheral must be designed to handle the μ DMA transfer completion interrupt. If the transfer uses the software μ DMA channel, then the completion interrupt occurs on the dedicated software μ DMA interrupt vector (see Table 9-6 on page 597).

When μDMA is enabled for a peripheral, the μDMA controller stops the normal transfer interrupts for a peripheral from reaching the interrupt controller (the interrupts are still reported in the peripheral's interrupt registers). Thus, when a large amount of data is transferred using μDMA , instead of receiving multiple interrupts from the peripheral as data flows, the interrupt controller receives only one interrupt when the transfer is complete. Unmasked peripheral error interrupts continue to be sent to the interrupt controller.

When a μDMA channel generates a completion interrupt, the CHIS bit corresponding to the peripheral channel is set in the **DMA Channel Interrupt Status (DMACHIS)** register (see page 632). This register can be used by the peripheral interrupt handler code to determine if the interrupt was caused by the μDMA channel or an error event reported by the peripheral's interrupt registers. The completion interrupt request from the μDMA controller is automatically cleared when the interrupt handler is activated.

If the μ DMA controller encounters a bus or memory protection error as it attempts to perform a data transfer, it disables the μ DMA channel that caused the error and generates an interrupt on the μ DMA error interrupt vector. The processor can read the **DMA Bus Error Clear (DMAERRCLR)** register to determine if an error is pending. The ERRCLR bit is set if an error occurred. The error can be cleared by writing a 1 to the ERRCLR bit.

Table 9-6 shows the dedicated interrupt assignments for the μDMA controller.

Table 9-6. µDMA Interrupt Assignments

Interrupt	Assignment	
46	μDMA Software Channel Transfer	
47	μDMA Error	

9.3 Initialization and Configuration

9.3.1 Module Initialization

Before the μ DMA controller can be used, it must be enabled in the System Control block and in the peripheral. The location of the channel control structure must also be programmed.

The following steps should be performed one time during system initialization:

- 1. Enable the μDMA clock using the **RCGCDMA** register (see page 333).
- 2. Enable the μDMA controller by setting the MASTEREN bit of the **DMA Configuration (DMACFG)** register.
- Program the location of the channel control table by writing the base address of the table to the DMA Channel Control Base Pointer (DMACTLBASE) register. The base address must be aligned on a 1024-byte boundary.

9.3.2 Configuring a Memory-to-Memory Transfer

μDMA channel 30 is dedicated for software-initiated transfers. However, any channel can be used for software-initiated, memory-to-memory transfer if the associated peripheral is not being used.

9.3.2.1 Configure the Channel Attributes

First, configure the channel attributes:

- 1. Program bit 30 of the DMA Channel Priority Set (DMAPRIOSET) or DMA Channel Priority Clear (DMAPRIOCLR) registers to set the channel to High priority or Default priority.
- 2. Set bit 30 of the **DMA Channel Primary Alternate Clear (DMAALTCLR)** register to select the primary channel control structure for this transfer.
- 3. Set bit 30 of the **DMA Channel Useburst Clear (DMAUSEBURSTCLR)** register to allow the μDMA controller to respond to single and burst requests.
- **4.** Set bit 30 of the **DMA Channel Request Mask Clear (DMAREQMASKCLR)** register to allow the μDMA controller to recognize requests for this channel.

9.3.2.2 Configure the Channel Control Structure

Now the channel control structure must be configured.

This example transfers 256 words from one memory buffer to another. Channel 30 is used for a software transfer, and the control structure for channel 30 is at offset 0x1E0 of the channel control table. The channel control structure for channel 30 is located at the offsets shown in Table 9-7.

Table 9-7. Channel Control Structure Offsets for Channel 30

Offset	Description
Control Table Base + 0x1E0	Channel 30 Source End Pointer
Control Table Base + 0x1E4	Channel 30 Destination End Pointer
Control Table Base + 0x1E8	Channel 30 Control Word

Configure the Source and Destination

The source and destination end pointers must be set to the last address for the transfer (inclusive).

- 1. Program the source end pointer at offset 0x1E0 to the address of the source buffer + 0x3FC.
- Program the destination end pointer at offset 0x1E4 to the address of the destination buffer + 0x3FC.

The control word at offset 0x1E8 must be programmed according to Table 9-8.

Table 9-8. Channel Control Word Configuration for Memory Transfer Example

Field in DMACHCTL	Bits	Value	Description
DSTINC	31:30	2	32-bit destination address increment
DSTSIZE	29:28	2	32-bit destination data size
SRCINC	27:26	2	32-bit source address increment
SRCSIZE	25:24	2	32-bit source data size
reserved	23:18	0	Reserved

Table 9-8. Channel Control Word Configuration for Memory Transfer Example (continued)

Field in DMACHCTL	Bits	Value	Description
ARBSIZE	17:14	3	Arbitrates after 8 transfers
XFERSIZE	13:4	255	Transfer 256 items
NXTUSEBURST	3	0	N/A for this transfer type
XFERMODE	2:0	2	Use Auto-request transfer mode

9.3.2.3 Start the Transfer

Now the channel is configured and is ready to start.

- Enable the channel by setting bit 30 of the DMA Channel Enable Set (DMAENASET) register.
- 2. Issue a transfer request by setting bit 30 of the **DMA Channel Software Request (DMASWREQ)** register.

The µDMA transfer begins. If the interrupt is enabled, then the processor is notified by interrupt when the transfer is complete. If needed, the status can be checked by reading bit 30 of the **DMAENASET** register. This bit is automatically cleared when the transfer is complete. The status can also be checked by reading the XFERMODE field of the channel control word at offset 0x1E8. This field is automatically cleared at the end of the transfer.

9.3.3 Configuring a Peripheral for Simple Transmit

This example configures the μ DMA controller to transmit a buffer of data to a peripheral. The peripheral has a transmit FIFO with a trigger level of 4. The example peripheral uses μ DMA channel 7.

9.3.3.1 Configure the Channel Attributes

First, configure the channel attributes:

- 1. Configure bit 7 of the **DMA Channel Priority Set (DMAPRIOSET)** or **DMA Channel Priority Clear (DMAPRIOCLR)** registers to set the channel to High priority or Default priority.
- 2. Set bit 7 of the **DMA Channel Primary Alternate Clear (DMAALTCLR)** register to select the primary channel control structure for this transfer.
- 3. Set bit 7 of the **DMA Channel Useburst Clear (DMAUSEBURSTCLR)** register to allow the µDMA controller to respond to single and burst requests.
- **4.** Set bit 7 of the **DMA Channel Request Mask Clear (DMAREQMASKCLR)** register to allow the µDMA controller to recognize requests for this channel.

9.3.3.2 Configure the Channel Control Structure

This example transfers 64 bytes from a memory buffer to the peripheral's transmit FIFO register using µDMA channel 7. The control structure for channel 7 is at offset 0x070 of the channel control table. The channel control structure for channel 7 is located at the offsets shown in Table 9-9.

Table 9-9. Channel Control Structure Offsets for Channel 7

Offset	Description
Control Table Base + 0x070	Channel 7 Source End Pointer

Table 9-9. Channel Control Structure Offsets for Channel 7 (continued)

Offset	Description
Control Table Base + 0x074	Channel 7 Destination End Pointer
Control Table Base + 0x078	Channel 7 Control Word

Configure the Source and Destination

The source and destination end pointers must be set to the last address for the transfer (inclusive). Because the peripheral pointer does not change, it simply points to the peripheral's data register.

- 1. Program the source end pointer at offset 0x070 to the address of the source buffer + 0x3F.
- **2.** Program the destination end pointer at offset 0x074 to the address of the peripheral's transmit FIFO register.

The control word at offset 0x078 must be programmed according to Table 9-10.

Table 9-10. Channel Control Word Configuration for Peripheral Transmit Example

Field in DMACHCTL	Bits	Value	Description
DSTINC	31:30	3	Destination address does not increment
DSTSIZE	29:28	0	8-bit destination data size
SRCINC	27:26	0	8-bit source address increment
SRCSIZE	25:24	0	8-bit source data size
reserved	23:18	0	Reserved
ARBSIZE	17:14	2	Arbitrates after 4 transfers
XFERSIZE	13:4	63	Transfer 64 items
NXTUSEBURST	3	0	N/A for this transfer type
XFERMODE	2:0	1	Use Basic transfer mode

Note: In this example, it is not important if the peripheral makes a single request or a burst request. Because the peripheral has a FIFO that triggers at a level of 4, the arbitration size is set to 4. If the peripheral does make a burst request, then 4 bytes are transferred, which is what the FIFO can accommodate. If the peripheral makes a single request (if there is any space in the FIFO), then one byte is transferred at a time. If it is important to the application that transfers only be made in bursts, then the Channel Useburst SET[7] bit should be set in the DMA Channel Useburst Set (DMAUSEBURSTSET) register.

9.3.3.3 Start the Transfer

Now the channel is configured and is ready to start.

Enable the channel by setting bit 7 of the DMA Channel Enable Set (DMAENASET) register.

The μDMA controller is now configured for transfer on channel 7. The controller makes transfers to the peripheral whenever the peripheral asserts a μDMA request. The transfers continue until the entire buffer of 64 bytes has been transferred. When that happens, the μDMA controller disables the channel and sets the XFERMODE field of the channel control word to 0 (Stopped). The status of the transfer can be checked by reading bit 7 of the **DMA Channel Enable Set (DMAENASET)** register. This bit is automatically cleared when the transfer is complete. The status can also be checked by reading the XFERMODE field of the channel control word at offset 0x078. This field is automatically cleared at the end of the transfer.

If peripheral interrupts are enabled, then the peripheral interrupt handler receives an interrupt when the entire transfer is complete.

9.3.4 Configuring a Peripheral for Ping-Pong Receive

This example configures the μ DMA controller to continuously receive 8-bit data from a peripheral into a pair of 64-byte buffers. The peripheral has a receive FIFO with a trigger level of 8. The example peripheral uses μ DMA channel 8.

9.3.4.1 Configure the Channel Attributes

First, configure the channel attributes:

- Configure bit 8 of the DMA Channel Priority Set (DMAPRIOSET) or DMA Channel Priority Clear (DMAPRIOCLR) registers to set the channel to High priority or Default priority.
- 2. Set bit 8 of the **DMA Channel Primary Alternate Clear (DMAALTCLR)** register to select the primary channel control structure for this transfer.
- 3. Set bit 8 of the **DMA Channel Useburst Clear (DMAUSEBURSTCLR)** register to allow the µDMA controller to respond to single and burst requests.
- **4.** Set bit 8 of the **DMA Channel Request Mask Clear (DMAREQMASKCLR)** register to allow the μDMA controller to recognize requests for this channel.

9.3.4.2 Configure the Channel Control Structure

This example transfers bytes from the peripheral's receive FIFO register into two memory buffers of 64 bytes each. As data is received, when one buffer is full, the μ DMA controller switches to use the other.

To use Ping-Pong buffering, both primary and alternate channel control structures must be used. The primary control structure for channel 8 is at offset 0x080 of the channel control table, and the alternate channel control structure is at offset 0x280. The channel control structures for channel 8 are located at the offsets shown in Table 9-11.

Table 9-11. Primary and Alternate Channel Control Structure Offsets for Channel 8

Offset	Description
Control Table Base + 0x080	Channel 8 Primary Source End Pointer
Control Table Base + 0x084	Channel 8 Primary Destination End Pointer
Control Table Base + 0x088	Channel 8 Primary Control Word
Control Table Base + 0x280	Channel 8 Alternate Source End Pointer
Control Table Base + 0x284	Channel 8 Alternate Destination End Pointer
Control Table Base + 0x288	Channel 8 Alternate Control Word

Configure the Source and Destination

The source and destination end pointers must be set to the last address for the transfer (inclusive). Because the peripheral pointer does not change, it simply points to the peripheral's data register. Both the primary and alternate sets of pointers must be configured.

 Program the primary source end pointer at offset 0x080 to the address of the peripheral's receive buffer.

- 2. Program the primary destination end pointer at offset 0x084 to the address of ping-pong buffer A + 0x3F.
- 3. Program the alternate source end pointer at offset 0x280 to the address of the peripheral's receive buffer.
- **4.** Program the alternate destination end pointer at offset 0x284 to the address of ping-pong buffer B + 0x3F.

The primary control word at offset 0x088 and the alternate control word at offset 0x288 are initially programmed the same way.

- 1. Program the primary channel control word at offset 0x088 according to Table 9-12.
- 2. Program the alternate channel control word at offset 0x288 according to Table 9-12.

Table 9-12. Channel Control Word Configuration for Peripheral Ping-Pong Receive Example

Field in DMACHCTL	Bits	Value	Description
DSTINC	31:30	0	8-bit destination address increment
DSTSIZE	29:28	0	8-bit destination data size
SRCINC	27:26	3	Source address does not increment
SRCSIZE	25:24	0	8-bit source data size
reserved	23:18	0	Reserved
ARBSIZE	17:14	3	Arbitrates after 8 transfers
XFERSIZE	13:4	63	Transfer 64 items
NXTUSEBURST	3	0	N/A for this transfer type
XFERMODE	2:0	3	Use Ping-Pong transfer mode

Note: In this example, it is not important if the peripheral makes a single request or a burst request. Because the peripheral has a FIFO that triggers at a level of 8, the arbitration size is set to 8. If the peripheral does make a burst request, then 8 bytes are transferred, which is what the FIFO can accommodate. If the peripheral makes a single request (if there is any data in the FIFO), then one byte is transferred at a time. If it is important to the application that transfers only be made in bursts, then the Channel Useburst SET[8] bit should be set in the DMA Channel Useburst Set (DMAUSEBURSTSET) register.

9.3.4.3 Configure the Peripheral Interrupt

An interrupt handler should be configured when using μ DMA Ping-Pong mode, it is best to use an interrupt handler. However, the Ping-Pong mode can be configured without interrupts by polling. The interrupt handler is triggered after each buffer is complete.

1. Configure and enable an interrupt handler for the peripheral.

9.3.4.4 Enable the µDMA Channel

Now the channel is configured and is ready to start.

1. Enable the channel by setting bit 8 of the DMA Channel Enable Set (DMAENASET) register.

9.3.4.5 Process Interrupts

The μ DMA controller is now configured and enabled for transfer on channel 8. When the peripheral asserts the μ DMA request signal, the μ DMA controller makes transfers into buffer A using the primary channel control structure. When the primary transfer to buffer A is complete, it switches to the alternate channel control structure and makes transfers into buffer B. At the same time, the primary channel control word mode field is configured to indicate Stopped, and an interrupt is pending.

When an interrupt is triggered, the interrupt handler must determine which buffer is complete and process the data or set a flag that the data must be processed by non-interrupt buffer processing code. Then the next buffer transfer must be set up.

In the interrupt handler:

- 1. Read the primary channel control word at offset 0x088 and check the XFERMODE field. If the field is 0, this means buffer A is complete. If buffer A is complete, then:
 - **a.** Process the newly received data in buffer A or signal the buffer processing code that buffer A has data available.
 - **b.** Reprogram the primary channel control word at offset 0x88 according to Table 9-12 on page 602.
- 2. Read the alternate channel control word at offset 0x288 and check the XFERMODE field. If the field is 0, this means buffer B is complete. If buffer B is complete, then:
 - a. Process the newly received data in buffer B or signal the buffer processing code that buffer B has data available.
 - **b.** Reprogram the alternate channel control word at offset 0x288 according to Table 9-12 on page 602.

9.3.5 Configuring Channel Assignments

Channel assignments for each μDMA channel can be changed using the **DMACHMAPn** registers. Each 4-bit field represents a μDMA channel.

Refer to Table 9-1 on page 584 for channel assignments.

9.4 Register Map

Table 9-13 on page 604 lists the μ DMA channel control structures and registers. The channel control structure shows the layout of one entry in the channel control table. The channel control table is located in system memory, and the location is determined by the application, thus, the base address is n/a (not applicable) and noted as so above the register descriptions. In the table below, the offset for the channel control structures is the offset from the entry in the channel control table. See "Channel Configuration" on page 586 and Table 9-3 on page 587 for a description of how the entries in the channel control table are located in memory. The μ DMA register addresses are given as a hexadecimal increment, relative to the μ DMA base address of 0x400F.F000. Note that the μ DMA module clock must be enabled before the registers can be programmed (see page 333). There must be a delay of 3 system clocks after the μ DMA module clock is enabled before any μ DMA module registers are accessed.

Table 9-13. µDMA Register Map

Offset	Name	Туре	Reset	Description	See page
μDMA Ch	annel Control Structure	(Offset fro	m Channel Control	Table Base)	
0x000	DMASRCENDP	R/W	-	DMA Channel Source Address End Pointer	606
0x004	DMADSTENDP	R/W	-	DMA Channel Destination Address End Pointer	607
0x008	DMACHCTL	R/W	-	DMA Channel Control Word	608
μDMA Re	gisters (Offset from µDN	IA Base Ac	ldress)		
0x000	DMASTAT	RO	0x001F.0000	DMA Status	613
0x004	DMACFG	WO	-	DMA Configuration	615
0x008	DMACTLBASE	R/W	0x0000.0000	DMA Channel Control Base Pointer	616
0x00C	DMAALTBASE	RO	0x0000.0200	DMA Alternate Channel Control Base Pointer	617
0x010	DMAWAITSTAT	RO	0x03C3.CF00	DMA Channel Wait-on-Request Status	618
0x014	DMASWREQ	WO	-	DMA Channel Software Request	619
0x018	DMAUSEBURSTSET	R/W	0x0000.0000	DMA Channel Useburst Set	620
0x01C	DMAUSEBURSTCLR	WO	-	DMA Channel Useburst Clear	621
0x020	DMAREQMASKSET	R/W	0x0000.0000	DMA Channel Request Mask Set	622
0x024	DMAREQMASKCLR	WO	-	DMA Channel Request Mask Clear	623
0x028	DMAENASET	R/W	0x0000.0000	DMA Channel Enable Set	624
0x02C	DMAENACLR	WO	-	DMA Channel Enable Clear	625
0x030	DMAALTSET	R/W	0x0000.0000	DMA Channel Primary Alternate Set	626
0x034	DMAALTCLR	WO	-	DMA Channel Primary Alternate Clear	627
0x038	DMAPRIOSET	R/W	0x0000.0000	DMA Channel Priority Set	628
0x03C	DMAPRIOCLR	WO	-	DMA Channel Priority Clear	629
0x04C	DMAERRCLR	R/W	0x0000.0000	DMA Bus Error Clear	630
0x500	DMACHASGN	R/W	0x0000.0000	DMA Channel Assignment	631
0x504	DMACHIS	R/W1C	0x0000.0000	DMA Channel Interrupt Status	632
0x510	DMACHMAP0	R/W	0x0000.0000	DMA Channel Map Select 0	633
0x514	DMACHMAP1	R/W	0x0000.0000	DMA Channel Map Select 1	634
0x518	DMACHMAP2	R/W	0x0000.0000	DMA Channel Map Select 2	635
0x51C	DMACHMAP3	R/W	0x0000.0000	DMA Channel Map Select 3	636
0xFD0	DMAPeriphID4	RO	0x0000.0004	DMA Peripheral Identification 4	641
0xFE0	DMAPeriphID0	RO	0x0000.0030	DMA Peripheral Identification 0	637
0xFE4	DMAPeriphID1	RO	0x0000.00B2	DMA Peripheral Identification 1	638
0xFE8	DMAPeriphID2	RO	0x0000.000B	DMA Peripheral Identification 2	639

Table 9-13. µDMA Register Map (continued)

Offset	Name	Type	Reset	Description	See page
0xFEC	DMAPeriphID3	RO	0x0000.0000	DMA Peripheral Identification 3	640
0xFF0	DMAPCellID0	RO	0x0000.000D	DMA PrimeCell Identification 0	642
0xFF4	DMAPCellID1	RO	0x0000.00F0	DMA PrimeCell Identification 1	643
0xFF8	DMAPCellID2	RO	0x0000.0005	DMA PrimeCell Identification 2	644
0xFFC	DMAPCellID3	RO	0x0000.00B1	DMA PrimeCell Identification 3	645

9.5 µDMA Channel Control Structure

The μ DMA Channel Control Structure holds the transfer settings for a μ DMA channel. Each channel has two control structures, which are located in a table in system memory. Refer to "Channel Configuration" on page 586 for an explanation of the Channel Control Table and the Channel Control Structure.

The channel control structure is one entry in the channel control table. Each channel has a primary and alternate structure. The primary control structures are located at offsets 0x0, 0x10, 0x20 and so on. The alternate control structures are located at offsets 0x200, 0x210, 0x220, and so on.

Register 1: DMA Channel Source Address End Pointer (DMASRCENDP), offset 0x000


DMA Channel Source Address End Pointer (DMASRCENDP) is part of the Channel Control Structure and is used to specify the source address for a µDMA transfer.

The μ DMA controller can transfer data to and from the on-chip SRAM. However, because the Flash memory and ROM are located on a separate internal bus, it is not possible to transfer data to/from the Flash memory or ROM with the μ DMA controller.

Note: The offset specified is from the base address of the control structure in system memory, not the µDMA module base address.

DMA Channel Source Address End Pointer (DMASRCENDP)

Base n/a Offset 0x000 Type R/W, reset -



This field points to the last address of the μDMA transfer source (inclusive). If the source address is not incrementing (the SRCINC field in the **DMACHCTL** register is 0x3), then this field points at the source location itself (such as a peripheral data register).


Register 2: DMA Channel Destination Address End Pointer (DMADSTENDP), offset 0x004

DMA Channel Destination Address End Pointer (DMADSTENDP) is part of the Channel Control Structure and is used to specify the destination address for a μ DMA transfer.

Note: The offset specified is from the base address of the control structure in system memory, not the μ DMA module base address.

DMA Channel Destination Address End Pointer (DMADSTENDP)

Base n/a Offset 0x004 Type R/W, reset -



This field points to the last address of the μDMA transfer destination (inclusive). If the destination address is not incrementing (the <code>DSTINC</code> field in the **DMACHCTL** register is 0x3), then this field points at the destination location itself (such as a peripheral data register).


Register 3: DMA Channel Control Word (DMACHCTL), offset 0x008

DMA Channel Control Word (DMACHCTL) is part of the Channel Control Structure and is used to specify parameters of a μ DMA transfer.

Note: The offset specified is from the base address of the control structure in system memory, not the μ DMA module base address.

DMA Channel Control Word (DMACHCTL)

Base n/a Offset 0x008 Type R/W, reset -



31:30 DSTINC R/W - Destination Address Increment

This field configures the destination address increment.

The address increment value must be equal or greater than the value of the destination size (${\tt DSTSIZE}$).

Value Description

0x0 Byte

Increment by 8-bit locations

0x1 Half-word

Increment by 16-bit locations

0x2 Word

Increment by 32-bit locations

0x3 No increment

Address remains set to the value of the Destination Address End Pointer (DMADSTENDP) for the channel

Bit/Field	Name	Туре	Reset	Description
29:28	DSTSIZE	R/W	-	Destination Data Size
				This field configures the destination item data size.
				Note: DSTSIZE must be the same as SRCSIZE.
				Value Description
				0x0 Byte
				8-bit data size
				0x1 Half-word
				16-bit data size
				0x2 Word
				32-bit data size
				0x3 Reserved
27:26	SRCINC	R/W	-	Source Address Increment
				This field configures the source address increment.
				The address increment value must be equal or greater than the value of the source size (SRCSIZE).
				Value Description
				0x0 Byte
				Increment by 8-bit locations
				0x1 Half-word
				Increment by 16-bit locations
				0x2 Word
				Increment by 32-bit locations
				0x3 No increment
				Address remains set to the value of the Source Address End Pointer (DMASRCENDP) for the channel
25:24	SRCSIZE	R/W	-	Source Data Size
				This field configures the source item data size.
				Note: DSTSIZE must be the same as SRCSIZE.
				Value Description
				0x0 Byte
				8-bit data size.
				0x1 Half-word
				16-bit data size.
				0x2 Word
				32-bit data size.
				0x3 Reserved
23:18	reserved	RO	-	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.

Bit/Field	Name	Туре	Reset	Description
17:14	ARBSIZE	R/W	-	Arbitration Size This field configures the number of transfers that can occur before the μ DMA controller re-arbitrates. The possible arbitration rate configurations represent powers of 2 and are shown below.
				Value Description
				0x0 1 Transfer
				Arbitrates after each µDMA transfer
				0x1 2 Transfers
				0x2 4 Transfers
				0x3 8 Transfers
				0x4 16 Transfers
				0x5 32 Transfers
				0x6 64 Transfers
				0x7 128 Transfers
				0x8 256 Transfers
				0x9 512 Transfers
				0xA-0xF 1024 Transfers
				In this configuration, no arbitration occurs during the μDMA transfer because the maximum transfer size is 1024.
13:4	XFERSIZE	R/W	-	Transfer Size (minus 1)
				This field configures the total number of items to transfer. The value of this field is 1 less than the number to transfer (value 0 means transfer 1 item). The maximum value for this 10-bit field is 1023 which represents a transfer size of 1024 items.
				The transfer size is the number of items, not the number of bytes. If the data size is 32 bits, then this value is the number of 32-bit words to transfer.
				The μDMA controller updates this field immediately prior to entering the arbitration process, so it contains the number of outstanding items that is necessary to complete the μDMA cycle.
3	NXTUSEBURST	R/W	-	Next Useburst This field controls whether the Useburst SET[n] bit is automatically set for the last transfer of a peripheral scatter-gather operation. Normally, for the last transfer, if the number of remaining items to transfer is less than the arbitration size, the μDMA controller uses single transfers to complete the transaction. If this bit is set, then the controller uses a burst transfer to complete the last transfer.

Bit/Field	Name	Туре	Reset	Description
2:0	XFERMODE	R/W		μDMA Transfer Mode This field configures the operating mode of the μDMA cycle. Refer to "Transfer Modes" on page 588 for a detailed explanation of transfer modes. Because this register is in system RAM, it has no reset value. Therefore, this field should be initialized to 0 before the channel is enabled. Value Description 0x0 Stop 0x1 Basic 0x2 Auto-Request 0x3 Ping-Pong 0x4 Memory Scatter-Gather 0x5 Alternate Memory Scatter-Gather 0x6 Peripheral Scatter-Gather

XFERMODE Bit Field Values.

Stop

Channel is stopped or configuration data is invalid. No more transfers can occur.

Basic

For each trigger (whether from a peripheral or a software request), the µDMA controller performs the number of transfers specified by the ARBSIZE field.

Auto-Request

The initial request (software- or peripheral-initiated) is sufficient to complete the entire transfer of XFERSIZE items without any further requests.

Ping-Pong

This mode uses both the primary and alternate control structures for this channel. When the number of transfers specified by the XFERSIZE field have completed for the current control structure (primary or alternate), the μ DMA controller switches to the other one. These switches continue until one of the control structures is not set to ping-pong mode. At that point, the μ DMA controller stops. An interrupt is generated on completion of the transfers configured by each control structure. See "Ping-Pong" on page 588.

Memory Scatter-Gather

When using this mode, the primary control structure for the channel is configured to allow a list of operations (tasks) to be performed. The source address pointer specifies the start of a table of tasks to be copied to the alternate control structure for this channel. The XFERMODE field for the alternate control structure should be configured to 0x5 (Alternate memory scatter-gather) to perform the task. When the task completes, the µDMA switches back to the primary channel control structure, which then copies the next task to the alternate control structure. This process continues until the table of tasks is empty. The last task must have an XFERMODE value other than 0x5. Note that for continuous operation, the last task can update the primary channel control structure back to the start of the list or to another list. See "Memory Scatter-Gather" on page 589.

Alternate Memory Scatter-Gather

This value must be used in the alternate channel control data structure when the µDMA controller operates in Memory Scatter-Gather mode.

Peripheral Scatter-Gather

This value must be used in the primary channel control data structure when the μDMA controller operates in Peripheral Scatter-Gather mode. In this mode, the μDMA controller operates exactly the same as in Memory Scatter-Gather mode, except that instead of performing the number of transfers specified by the XFERSIZE field in the alternate control structure at one time, the μDMA controller only performs the number of transfers specified by the ARBSIZE field per trigger; see Basic mode for details. See "Peripheral Scatter-Gather" on page 593.

Alternate Peripheral Scatter-Gather

This value must be used in the alternate channel control data structure when the µDMA controller operates in Peripheral Scatter-Gather mode.

9.6 µDMA Register Descriptions

The register addresses given are relative to the µDMA base address of 0x400F.F000.

Register 4: DMA Status (DMASTAT), offset 0x000

The DMA Status (DMASTAT) register returns the status of the µDMA controller. You cannot read this register when the µDMA controller is in the reset state.

DMA Status (DMASTAT)


3:1

reserved

RO

0x0

Base 0x400F.F000 Offset 0x000 Type RO, reset 0x001F.0000



Bit/Field	Name	Туре	Reset	Description
31:21	reserved	RO	0x000	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
20:16	DMACHANS	RO	0x1F	Available µDMA Channels Minus 1
				This field contains a value equal to the number of μ DMA channels the μ DMA controller is configured to use, minus one. The value of 0x1F corresponds to 32 μ DMA channels.
15:8	reserved	RO	0x00	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
7:4	STATE	RO	0x0	Control State Machine Status
				This field shows the current status of the control state machine. Status can be one of the following.
				Value Description
				0x0 Idle
				0x1 Reading channel controller data.

Value	Description
0x0	Idle
0x1	Reading channel controller data.
0x2	Reading source end pointer.
0x3	Reading destination end pointer.
0x4	Reading source data.
0x5	Writing destination data.
0x6	Waiting for μDMA request to clear.
0x7	Writing channel controller data.
8x0	Stalled
0x9	Done
0xA-0xF	Undefined
Coffwore	

Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.


Bit/Field	Name	Type	Reset	Description
0	MASTEN	RO	0	Master Enable Status
				Value Description
				0 The μDMA controller is disabled.
				1 The μ DMA controller is enabled.

Register 5: DMA Configuration (DMACFG), offset 0x004

The **DMACFG** register controls the configuration of the µDMA controller.

DMA Configuration (DMACFG)

Base 0x400F.F000 Offset 0x004 Type WO, reset -



Bit/Field	Name	Type	Reset	Description
31:1	reserved	WO	-	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
0	MASTEN	WO		Controller Master Enable

Value Description

0 Disables the μDMA controller.

Enables μDMA controller.

Register 6: DMA Channel Control Base Pointer (DMACTLBASE), offset 0x008


The **DMACTLBASE** register must be configured so that the base pointer points to a location in system memory.

The amount of system memory that must be assigned to the µDMA controller depends on the number of µDMA channels used and whether the alternate channel control data structure is used. See "Channel Configuration" on page 586 for details about the Channel Control Table. The base address must be aligned on a 1024-byte boundary. This register cannot be read when the µDMA controller is in the reset state.

DMA Channel Control Base Pointer (DMACTLBASE)

Base 0x400F.F000

Offset 0x008 Type R/W, reset 0x0000.0000




Bit/Field	Name	Туре	Reset	Description
31:10	ADDR	R/W	0x0000.00	Channel Control Base Address This field contains the pointer to the base address of the channel control table. The base address must be 1024-byte aligned.
9:0	reserved	RO	0x00	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.

Register 7: DMA Alternate Channel Control Base Pointer (DMAALTBASE), offset 0x00C

The **DMAALTBASE** register returns the base address of the alternate channel control data. This register removes the necessity for application software to calculate the base address of the alternate channel control structures. This register cannot be read when the μDMA controller is in the reset state.

DMA Alternate Channel Control Base Pointer (DMAALTBASE)

Base 0x400F.F000 Offset 0x00C Type RO, reset 0x0000.0200



Bit/Field Name Type Reset Description

31:0 ADDR RO 0x0000.0200 Alternate Channel Address Pointer


This field provides the base address of the alternate channel control structures.

Register 8: DMA Channel Wait-on-Request Status (DMAWAITSTAT), offset 0x010

This read-only register indicates that the µDMA channel is waiting on a request. A peripheral can hold off the µDMA from performing a single request until the peripheral is ready for a burst request to enhance the µDMA performance. The use of this feature is dependent on the design of the peripheral and is not controllable by software in any way. This register cannot be read when the µDMA controller is in the reset state.

DMA Channel Wait-on-Request Status (DMAWAITSTAT)

Base 0x400F.F000 Offset 0x010 Type RO, reset 0x03C3.CF00



31:0 WAITREQ[n] RO 0x03C3.CF00 Channel [n] Wait Status

> These bits provide the channel wait-on-request status. Bit 0 corresponds to channel 0.

Value Description


- 1 The corresponding channel is waiting on a request.
- 0 The corresponding channel is not waiting on a request.

Register 9: DMA Channel Software Request (DMASWREQ), offset 0x014

Each bit of the **DMASWREQ** register represents the corresponding μ DMA channel. Setting a bit generates a request for the specified μ DMA channel.

DMA Channel Software Request (DMASWREQ)

Base 0x400F.F000 Offset 0x014 Type WO, reset -



31:0 SWREQ[n] WO - Channel [n] Software Request

These bits generate software requests. Bit 0 corresponds to channel 0.

Value Description

- 1 Generate a software request for the corresponding channel.
- 0 No request generated.

These bits are automatically cleared when the software request has been completed.

Register 10: DMA Channel Useburst Set (DMAUSEBURSTSET), offset 0x018

Each bit of the **DMAUSEBURSTSET** register represents the corresponding µDMA channel. Setting a bit disables the channel's single request input from generating requests, configuring the channel to only accept burst requests. Reading the register returns the status of USEBURST.


If the amount of data to transfer is a multiple of the arbitration (burst) size, the corresponding SET[n] bit is cleared after completing the final transfer. If there are fewer items remaining to transfer than the arbitration (burst) size, the μDMA controller automatically clears the corresponding SET[n] bit, allowing the remaining items to transfer using single requests. In order to resume transfers using burst requests, the corresponding bit must be set again. A bit should not be set if the corresponding peripheral does not support the burst request model.

Refer to "Request Types" on page 585 for more details about request types.

DMA Channel Useburst Set (DMAUSEBURSTSET)

Base 0x400F.F000

Offset 0x018 Type R/W, reset 0x0000.0000



Value Description

- 0 μ DMA channel [n] responds to single or burst requests.
- 1 µDMA channel [n] responds only to burst requests.

Bit 0 corresponds to channel 0. This bit is automatically cleared as described above. A bit can also be manually cleared by setting the corresponding ${\tt CLR[n]}$ bit in the **DMAUSEBURSTCLR** register.

Register 11: DMA Channel Useburst Clear (DMAUSEBURSTCLR), offset 0x01C

Each bit of the **DMAUSEBURSTCLR** register represents the corresponding μ DMA channel. Setting a bit clears the corresponding SET[n] bit in the **DMAUSEBURSTSET** register.


DMA Channel Useburst Clear (DMAUSEBURSTCLR)

CLR[n]

WO

Base 0x400F.F000 Offset 0x01C Type WO, reset -

31:0



Channel [n] Useburst Clear
Value Description

0 No effect.

1 Setting a bit clears the corresponding SET[n] bit in the **DMAUSEBURSTSET** register meaning that μDMA channel [n] responds to single and burst requests.

February 20, 2013 621


Register 12: DMA Channel Request Mask Set (DMAREQMASKSET), offset 0x020

Each bit of the **DMAREQMASKSET** register represents the corresponding μ DMA channel. Setting a bit disables μ DMA requests for the channel. Reading the register returns the request mask status. When a μ DMA channel's request is masked, that means the peripheral can no longer request μ DMA transfers. The channel can then be used for software-initiated transfers.

DMA Channel Request Mask Set (DMAREQMASKSET)

Base 0x400F.F000 Offset 0x020

Type R/W, reset 0x0000.0000



Value Description

- The peripheral associated with channel [n] is enabled to request μDMA transfers.
- The peripheral associated with channel [n] is not able to request μ DMA transfers. Channel [n] may be used for software-initiated transfers.


Bit 0 corresponds to channel 0. A bit can only be cleared by setting the corresponding $\mathtt{CLR}[n]$ bit in the **DMAREQMASKCLR** register.

Register 13: DMA Channel Request Mask Clear (DMAREQMASKCLR), offset 0x024

Each bit of the **DMAREQMASKCLR** register represents the corresponding μ DMA channel. Setting a bit clears the corresponding SET[n] bit in the **DMAREQMASKSET** register.

DMA Channel Request Mask Clear (DMAREQMASKCLR)

Base 0x400F.F000 Offset 0x024 Type WO, reset -



Value Description

- 0 No effect.
- 1 Setting a bit clears the corresponding SET[n] bit in the **DMAREQMASKSET** register meaning that the peripheral associated with channel [n] is enabled to request µDMA transfers.


Register 14: DMA Channel Enable Set (DMAENASET), offset 0x028

Each bit of the **DMAENASET** register represents the corresponding μ DMA channel. Setting a bit enables the corresponding μ DMA channel. Reading the register returns the enable status of the channels. If a channel is enabled but the request mask is set (**DMAREQMASKSET**), then the channel can be used for software-initiated transfers.

DMA Channel Enable Set (DMAENASET)

Base 0x400F.F000

Offset 0x028 Type R/W, reset 0x0000.0000



Value Description

0 μDMA Channel [n] is disabled.

1 μDMA Channel [n] is enabled.

Bit 0 corresponds to channel 0. A bit can only be cleared by setting the corresponding $\mathtt{CLR[n]}$ bit in the **DMAENACLR** register or when the end of a μDMA transfer occurs.

Register 15: DMA Channel Enable Clear (DMAENACLR), offset 0x02C

Each bit of the **DMAENACLR** register represents the corresponding μ DMA channel. Setting a bit clears the corresponding SET[n] bit in the **DMAENASET** register.


DMA Channel Enable Clear (DMAENACLR)

CLR[n]

WO

Base 0x400F.F000 Offset 0x02C Type WO, reset -

31:0



Value Description

Clear Channel [n] Enable Clear

0 No effect.

Setting a bit clears the corresponding SET[n] bit in the DMAENASET register meaning that channel [n] is disabled for μDMA transfers.

 $\begin{tabular}{ll} \textbf{Note:} & The controller disables a channel when it completes the μDMA cycle. \end{tabular}$


Register 16: DMA Channel Primary Alternate Set (DMAALTSET), offset 0x030

Each bit of the **DMAALTSET** register represents the corresponding μ DMA channel. Setting a bit configures the μ DMA channel to use the alternate control data structure. Reading the register returns the status of which control data structure is in use for the corresponding μ DMA channel.

DMA Channel Primary Alternate Set (DMAALTSET)

Base 0x400F.F000 Offset 0x030

Type R/W, reset 0x0000.0000



Value Description

- 0 μDMA channel [n] is using the primary control structure.
- 1 μDMA channel [n] is using the alternate control structure.

Bit 0 corresponds to channel 0. A bit can only be cleared by setting the corresponding CLR[n] bit in the **DMAALTCLR** register.

Note:


For Ping-Pong and Scatter-Gather cycle types, the µDMA controller automatically sets these bits to select the alternate channel control data structure.

Register 17: DMA Channel Primary Alternate Clear (DMAALTCLR), offset 0x034

Each bit of the **DMAALTCLR** register represents the corresponding μ DMA channel. Setting a bit clears the corresponding SET[n] bit in the **DMAALTSET** register.

DMA Channel Primary Alternate Clear (DMAALTCLR)

Base 0x400F.F000 Offset 0x034 Type WO, reset -



Value Description

0 No effect.

Setting a bit clears the corresponding SET[n] bit in the DMAALTSET register meaning that channel [n] is using the primary control structure.

Note: For Ping-Pong and Scatter-Gather cycle types, the µDMA controller automatically sets these bits to select the alternate channel control data structure.

February 20, 2013 627


Register 18: DMA Channel Priority Set (DMAPRIOSET), offset 0x038

Each bit of the **DMAPRIOSET** register represents the corresponding µDMA channel. Setting a bit configures the µDMA channel to have a high priority level. Reading the register returns the status of the channel priority mask.

DMA Channel Priority Set (DMAPRIOSET)

Base 0x400F.F000

Offset 0x038
Type R/W, reset 0x0000.0000



Bit/Field Description Name Type Reset 31:0 SET[n] R/W 0x0000.0000 Channel [n] Priority Set

Value Description

- µDMA channel [n] is using the default priority level.
- 1 μDMA channel [n] is using a high priority level.


Bit 0 corresponds to channel 0. A bit can only be cleared by setting the corresponding CLR[n] bit in the **DMAPRIOCLR** register.

Register 19: DMA Channel Priority Clear (DMAPRIOCLR), offset 0x03C

Each bit of the **DMAPRIOCLR** register represents the corresponding μ DMA channel. Setting a bit clears the corresponding SET[n] bit in the **DMAPRIOSET** register.

DMA Channel Priority Clear (DMAPRIOCLR)

Base 0x400F.F000 Offset 0x03C Type WO, reset -



Bit/Field Name Type Reset Description

31:0 CLR[n] WO - Channel [n] Priority Clear

Value Description

0 No effect.

Setting a bit clears the corresponding SET[n] bit in the DMAPRIOSET register meaning that channel [n] is using the default priority level.


Register 20: DMA Bus Error Clear (DMAERRCLR), offset 0x04C

The **DMAERRCLR** register is used to read and clear the μ DMA bus error status. The error status is set if the μ DMA controller encountered a bus error while performing a transfer. If a bus error occurs on a channel, that channel is automatically disabled by the μ DMA controller. The other channels are unaffected.

DMA Bus Error Clear (DMAERRCLR)

Base 0x400F.F000

Offset 0x04C Type R/W, reset 0x0000.0000



Bit/Field	Name	Type	Reset	Description
31:1	reserved	RO	0x0000.000	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
0	ERRCLR	R/W1C	0	μDMA Bus Error Status

Value Description

0 No bus error is pending.

A bus error is pending.

This bit is cleared by writing a 1 to it.


Register 21: DMA Channel Assignment (DMACHASGN), offset 0x500

Each bit of the **DMACHASGN** register represents the corresponding µDMA channel. Setting a bit selects the secondary channel assignment as specified in Table 9-1 on page 584.

This register is provided to support legacy software. New software should use the **DMACHMAPn** registers. If a bit is clear in this register, the corresponding field in the **DMACHMAPn** registers is configured to 0x0. If a bit is set in this register, the corresponding field is configured to 0x1. If this register is read, a bit reads as 0 if the corresponding **DMACHMAPn** register field value is equal to 0, otherwise it reads as 1 if the corresponding **DMACHMAPn** register field value is not equal to 0.

DMA Channel Assignment (DMACHASGN)

Base 0x400F.F000 Offset 0x500 Type R/W, reset 0x0000.0000



31:0 CHASGN[n] R/W - Channel [n] Assignment Select

Value Description

- 0 Use the primary channel assignment.
- 1 Use the secondary channel assignment.


Register 22: DMA Channel Interrupt Status (DMACHIS), offset 0x504

Each bit of the **DMACHIS** register represents the corresponding µDMA channel. A bit is set when that µDMA channel causes a completion interrupt. The bits are cleared by a writing a 1.

DMA Channel Interrupt Status (DMACHIS)

Base 0x400F.F000

Offset 0x504 Type R/W1C, reset 0x0000.0000



Value Description

- 1 The corresponding μDMA channel caused an interrupt.
- 0 The corresponding µDMA channel has not caused an interrupt.

This bit is cleared by writing a 1 to it.

Register 23: DMA Channel Map Select 0 (DMACHMAP0), offset 0x510

Each 4-bit field of the DMACHMAP0 register configures the µDMA channel assignment as specified in Table 9-1 on page 584.

To support legacy software which uses the **DMA Channel Assignment (DMACHASGN)** register, a value of 0x0 is equivalent to a **DMACHASGN** bit being clear, and a value of 0x1 is equivalent to a **DMACHASGN** bit being set.

DMA Channel Map Select 0 (DMACHMAP0)

Base 0x400F.F000

Offset 0x510
Type R/W, reset 0x0000.0000

_	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16
ſ		CH7	SEL	1		CH6	SEL	1		CH5	SEL	1		CH4	SEL	,
Type	R/W	R/W	R/W	R/W	R/W	R/W	R/W	R/W	R/W	R/W	R/W	R/W	R/W	R/W	R/W	R/W
Reset	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0
	15	14	13	12	11	10	9	8	7	6	5	4	3	2	1	0
		CH3	SSEL	ı		CH2	SEL	•		CH1	SEL	•		CHO	I SEL	1
Туре	R/W	R/W	R/W	R/W	R/W	R/W	R/W	R/W	R/W	R/W	R/W	R/W	R/W	R/W	R/W	R/W
Reset	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0

Bit/Field	Name	Туре	Reset	Description
31:28	CH7SEL	R/W	0x00	μDMA Channel 7 Source Select See Table 9-1 on page 584 for channel assignments.
27:24	CH6SEL	R/W	0x00	μDMA Channel 6 Source Select See Table 9-1 on page 584 for channel assignments.
23:20	CH5SEL	R/W	0x00	μDMA Channel 5 Source Select See Table 9-1 on page 584 for channel assignments.
19:16	CH4SEL	R/W	0x00	μDMA Channel 4 Source Select See Table 9-1 on page 584 for channel assignments.
15:12	CH3SEL	R/W	0x00	μDMA Channel 3 Source Select See Table 9-1 on page 584 for channel assignments.
11:8	CH2SEL	R/W	0x00	μDMA Channel 2 Source Select See Table 9-1 on page 584 for channel assignments.
7:4	CH1SEL	R/W	0x00	μDMA Channel 1 Source Select See Table 9-1 on page 584 for channel assignments.
3:0	CH0SEL	R/W	0x00	μDMA Channel 0 Source Select See Table 9-1 on page 584 for channel assignments.

Register 24: DMA Channel Map Select 1 (DMACHMAP1), offset 0x514

Each 4-bit field of the DMACHMAP1 register configures the µDMA channel assignment as specified in Table 9-1 on page 584.

To support legacy software which uses the **DMA Channel Assignment (DMACHASGN)** register, a value of 0x0 is equivalent to a **DMACHASGN** bit being clear, and a value of 0x1 is equivalent to a **DMACHASGN** bit being set.

DMA Channel Map Select 1 (DMACHMAP1)

Base 0x400F.F000 Offset 0x514 Type R/W, reset 0x0000.0000

	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16
		CH1	SSEL			CH1	4SEL	ı		CH1	BSEL	1		CH12	2SEL	'
Type Reset	R/W 0	R/W 0	R/W 0	R/W 0	R/W 0	R/W 0	R/W 0	R/W 0	R/W 0	R/W 0	R/W 0	R/W 0	R/W 0	R/W 0	R/W 0	R/W 0
	15	14	13	12	11	10	9	8	7	6	5	4	3	2	1	0
		CH1	I ISEL			CH1	0SEL	•		CH9	SEL	•		CH8	SEL	'
Type Reset	R/W 0	R/W 0	R/W 0	R/W 0	R/W 0	R/W 0	R/W 0	R/W 0	R/W 0	R/W 0	R/W 0	R/W 0	R/W 0	R/W 0	R/W 0	R/W 0

Bit/Field	Name	Туре	Reset	Description
31:28	CH15SEL	R/W	0x00	μDMA Channel 15 Source Select See Table 9-1 on page 584 for channel assignments.
27:24	CH14SEL	R/W	0x00	μDMA Channel 14 Source Select See Table 9-1 on page 584 for channel assignments.
23:20	CH13SEL	R/W	0x00	μDMA Channel 13 Source Select See Table 9-1 on page 584 for channel assignments.
19:16	CH12SEL	R/W	0x00	μDMA Channel 12 Source Select See Table 9-1 on page 584 for channel assignments.
15:12	CH11SEL	R/W	0x00	μDMA Channel 11 Source Select See Table 9-1 on page 584 for channel assignments.
11:8	CH10SEL	R/W	0x00	μDMA Channel 10 Source Select See Table 9-1 on page 584 for channel assignments.
7:4	CH9SEL	R/W	0x00	μDMA Channel 9 Source Select See Table 9-1 on page 584 for channel assignments.
3:0	CH8SEL	R/W	0x00	μDMA Channel 8 Source Select See Table 9-1 on page 584 for channel assignments.

Register 25: DMA Channel Map Select 2 (DMACHMAP2), offset 0x518

Each 4-bit field of the DMACHMAP2 register configures the µDMA channel assignment as specified in Table 9-1 on page 584.

To support legacy software which uses the **DMA Channel Assignment (DMACHASGN)** register, a value of 0x0 is equivalent to a **DMACHASGN** bit being clear, and a value of 0x1 is equivalent to a **DMACHASGN** bit being set.

DMA Channel Map Select 2 (DMACHMAP2)

Base 0x400F.F000

Offset 0x518
Type R/W, reset 0x0000.0000

	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16
		CH2	3SEL	1		CH2:	2SEL	1		CH2	1SEL	1		CH2	OSEL	,
Type	R/W	R/W	R/W	R/W	R/W	R/W	R/W	R/W	R/W	R/W	R/W	R/W	R/W	R/W	R/W	R/W
Reset	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0
_	15	14	13	12	11	10	9	8	7	6	5	4	3	2	1	0
		CH19	9SEL	ı		CH1	8SEL	1		CH1	7SEL	ı		CH1	SSEL	
Туре	R/W	R/W	R/W	R/W	R/W	R/W	R/W	R/W	R/W	R/W	R/W	R/W	R/W	R/W	R/W	R/W
Reset	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0

Bit/Field	Name	Туре	Reset	Description
31:28	CH23SEL	R/W	0x00	μDMA Channel 23 Source Select See Table 9-1 on page 584 for channel assignments.
27:24	CH22SEL	R/W	0x00	μDMA Channel 22 Source Select See Table 9-1 on page 584 for channel assignments.
23:20	CH21SEL	R/W	0x00	μDMA Channel 21 Source Select See Table 9-1 on page 584 for channel assignments.
19:16	CH20SEL	R/W	0x00	μDMA Channel 20 Source Select See Table 9-1 on page 584 for channel assignments.
15:12	CH19SEL	R/W	0x00	μDMA Channel 19 Source Select See Table 9-1 on page 584 for channel assignments.
11:8	CH18SEL	R/W	0x00	μDMA Channel 18 Source Select See Table 9-1 on page 584 for channel assignments.
7:4	CH17SEL	R/W	0x00	μDMA Channel 17 Source Select See Table 9-1 on page 584 for channel assignments.
3:0	CH16SEL	R/W	0x00	μDMA Channel 16 Source Select See Table 9-1 on page 584 for channel assignments.

Register 26: DMA Channel Map Select 3 (DMACHMAP3), offset 0x51C

Each 4-bit field of the DMACHMAP3 register configures the µDMA channel assignment as specified in Table 9-1 on page 584.

To support legacy software which uses the **DMA Channel Assignment (DMACHASGN)** register, a value of 0x0 is equivalent to a **DMACHASGN** bit being clear, and a value of 0x1 is equivalent to a **DMACHASGN** bit being set.

DMA Channel Map Select 3 (DMACHMAP3)

Base 0x400F.F000 Offset 0x51C Type R/W, reset 0x0000.0000

	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16
		CH3	I 1SEL	1		CH3	0SEL	1		CH29	9SEL	1		CH2	8SEL	
Type	R/W	R/W	R/W	R/W	R/W	R/W	R/W	R/W	R/W	R/W	R/W	R/W	R/W	R/W	R/W	R/W
Reset	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0
_	15	14	13	12	11	10	9	8	7	6	5	4	3	2	1	0
	CH27SEL CH26SEL				CH2	SSEL	1		CH2	4SEL						
Type	R/W	R/W	R/W	R/W	R/W	R/W	R/W	R/W	R/W	R/W	R/W	R/W	R/W	R/W	R/W	R/W
Reset	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0


Bit/Field	Name	Туре	Reset	Description
31:28	CH31SEL	R/W	0x00	μDMA Channel 31 Source Select See Table 9-1 on page 584 for channel assignments.
27:24	CH30SEL	R/W	0x00	μDMA Channel 30 Source Select See Table 9-1 on page 584 for channel assignments.
23:20	CH29SEL	R/W	0x00	μDMA Channel 29 Source Select See Table 9-1 on page 584 for channel assignments.
19:16	CH28SEL	R/W	0x00	μDMA Channel 28 Source Select See Table 9-1 on page 584 for channel assignments.
15:12	CH27SEL	R/W	0x00	μDMA Channel 27 Source Select See Table 9-1 on page 584 for channel assignments.
11:8	CH26SEL	R/W	0x00	μDMA Channel 26 Source Select See Table 9-1 on page 584 for channel assignments.
7:4	CH25SEL	R/W	0x00	μDMA Channel 25 Source Select See Table 9-1 on page 584 for channel assignments.
3:0	CH24SEL	R/W	0x00	μDMA Channel 24 Source Select See Table 9-1 on page 584 for channel assignments.

Register 27: DMA Peripheral Identification 0 (DMAPeriphID0), offset 0xFE0

The **DMAPeriphIDn** registers are hard-coded, and the fields within the registers determine the reset values.

DMA Peripheral Identification 0 (DMAPeriphID0)

Base 0x400F.F000 Offset 0xFE0 Type RO, reset 0x0000.0030



Bit/Field	Name	Type	Reset	Description
31:8	reserved	RO	0x0000.00	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
7:0	PID0	RO	0x30	μDMA Peripheral ID Register [7:0]
				Can be used by software to identify the presence of this peripheral.


February 20, 2013 637

Register 28: DMA Peripheral Identification 1 (DMAPeriphID1), offset 0xFE4

The **DMAPeriphIDn** registers are hard-coded, and the fields within the registers determine the reset values.

DMA Peripheral Identification 1 (DMAPeriphID1)

Base 0x400F.F000 Offset 0xFE4 Type RO, reset 0x0000.00B2




Bit/Field	Name	Type	Reset	Description
31:8	reserved	RO	0x0000.00	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
7:0	PID1	RO	0xB2	μDMA Peripheral ID Register [15:8] Can be used by software to identify the presence of this peripheral.

Register 29: DMA Peripheral Identification 2 (DMAPeriphID2), offset 0xFE8

The **DMAPeriphIDn** registers are hard-coded, and the fields within the registers determine the reset values.

DMA Peripheral Identification 2 (DMAPeriphID2)

Base 0x400F.F000 Offset 0xFE8 Type RO, reset 0x0000.000B



Bit/Field	Name	Type	Reset	Description
31:8	reserved	RO	0x0000.00	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
7:0	PID2	RO	0x0B	μDMA Peripheral ID Register [23:16]
				Can be used by software to identify the presence of this peripheral.


February 20, 2013 639

Register 30: DMA Peripheral Identification 3 (DMAPeriphID3), offset 0xFEC

The **DMAPeriphIDn** registers are hard-coded and the fields within the registers determine the reset values.

DMA Peripheral Identification 3 (DMAPeriphID3)

Base 0x400F.F000 Offset 0xFEC Type RO, reset 0x0000.0000



Bit/Field	Name	Type	Reset	Description
31:8	reserved	RO	0x0000.00	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
7:0	PID3	RO	0x00	μDMA Peripheral ID Register [31:24]


Can be used by software to identify the presence of this peripheral.

Register 31: DMA Peripheral Identification 4 (DMAPeriphID4), offset 0xFD0

The **DMAPeriphIDn** registers are hard-coded, and the fields within the registers determine the reset values.

DMA Peripheral Identification 4 (DMAPeriphID4)

Base 0x400F.F000 Offset 0xFD0 Type RO, reset 0x0000.0004




Bit/Field	Name	Type	Reset	Description
31:8	reserved	RO	0x0000.00	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
7:0	PID4	RO	0x04	μDMA Peripheral ID Register Can be used by software to identify the presence of this peripheral.

Register 32: DMA PrimeCell Identification 0 (DMAPCellID0), offset 0xFF0

The **DMAPCellIDn** registers are hard-coded, and the fields within the registers determine the reset values.

DMA PrimeCell Identification 0 (DMAPCellID0)

Base 0x400F.F000 Offset 0xFF0 Type RO, reset 0x0000.000D




Bit/Field	Name	Type	Reset	Description
31:8	reserved	RO	0x0000.00	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
7:0	CID0	RO	0x0D	μDMA PrimeCell ID Register [7:0]

Register 33: DMA PrimeCell Identification 1 (DMAPCellID1), offset 0xFF4

The **DMAPCellIDn** registers are hard-coded, and the fields within the registers determine the reset values.

DMA PrimeCell Identification 1 (DMAPCellID1)

Base 0x400F.F000 Offset 0xFF4 Type RO, reset 0x0000.00F0




Bit/Field	Name	Type	Reset	Description
31:8	reserved	RO	0x0000.00	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
7:0	CID1	RO	0xF0	μDMA PrimeCell ID Register [15:8]

Register 34: DMA PrimeCell Identification 2 (DMAPCellID2), offset 0xFF8

The **DMAPCellIDn** registers are hard-coded, and the fields within the registers determine the reset values.

DMA PrimeCell Identification 2 (DMAPCellID2)

Base 0x400F.F000 Offset 0xFF8 Type RO, reset 0x0000.0005




Bit/Field	Name	Type	Reset	Description
31:8	reserved	RO	0x00	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
7:0	CID2	RO	0x05	μDMA PrimeCell ID Register [23:16]

Register 35: DMA PrimeCell Identification 3 (DMAPCellID3), offset 0xFFC

The **DMAPCellIDn** registers are hard-coded, and the fields within the registers determine the reset values.

DMA PrimeCell Identification 3 (DMAPCellID3)

Base 0x400F.F000 Offset 0xFFC Type RO, reset 0x0000.00B1



Bit/Field	Name	Type	Reset	Description
31:8	reserved	RO	0x00	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
7:0	CID3	RO	0xB1	μDMA PrimeCell ID Register [31:24]

10 General-Purpose Input/Outputs (GPIOs)

The GPIO module is composed of ten physical GPIO blocks, each corresponding to an individual GPIO port (Port A, Port B, Port C, Port D, Port E, Port F, Port G, Port H, Port J, Port K, Port L). The GPIO module supports up to 69 programmable input/output pins, depending on the peripherals being used.

The GPIO module has the following features:

- Up to 69 GPIOs, depending on configuration
- Highly flexible pin muxing allows use as GPIO or one of several peripheral functions
- 5-V-tolerant in input configuration
- Fast toggle capable of a change every clock cycle for ports on AHB, every two clock cycles for ports on APB
- Programmable control for GPIO interrupts
 - Interrupt generation masking
 - Edge-triggered on rising, falling, or both
 - Level-sensitive on High or Low values
- Bit masking in both read and write operations through address lines
- Can be used to initiate an ADC sample sequence or a µDMA transfer
- Pin state can be retained during Hibernation mode
- Pins configured as digital inputs are Schmitt-triggered
- Programmable control for GPIO pad configuration
 - Weak pull-up or pull-down resistors
 - 2-mA, 4-mA, and 8-mA pad drive for digital communication; up to four pads can sink 18-mA for high-current applications
 - Slew rate control for 8-mA pad drive
 - Open drain enables
 - Digital input enables

10.1 Signal Description

GPIO signals have alternate hardware functions. The following table lists the GPIO pins and their analog and digital alternate functions. All GPIO signals are 5-V tolerant when configured as inputs except for PJO, PJI, PBO and PBI, which are limited to 3.6 V. The digital alternate hardware functions are enabled by setting the appropriate bit in the **GPIO Alternate Function Select (GPIOAFSEL)** and **GPIODEN** registers and configuring the PMCx bit field in the **GPIO Port Control (GPIOPCTL)** register to the numeric encoding shown in the table below. Analog signals in the table below are

also 5-V tolerant and are configured by clearing the DEN bit in the **GPIO Digital Enable (GPIODEN)** register. The AINx analog signals have internal circuitry to protect them from voltages over V_{DD} (up to the maximum specified in Table 24-4 on page 1377), but analog performance specifications are only guaranteed if the input signal swing at the I/O pad is kept inside the range 0 V < V_{IN} < V_{DD} . Note that each pin must be programmed individually; no type of grouping is implied by the columns in the table. Table entries that are shaded gray are the default values for the corresponding GPIO pin.

Important: All GPIO pins are configured as GPIOs and tri-stated by default (GPIOAFSEL=0, GPIODEN=0, GPIOPDR=0, GPIOPUR=0, and GPIOPCTL=0), with the exception of the pins shown in the table below. A Power-On-Reset (POR) or asserting RST puts the pins back to their default state.

Table 10-1, GPIO Pins With Non-Zero Reset Values

GPIO Pins	Default State	GPIOAFSEL	GPIODEN	GPIOPDR	GPIOPUR	GPIOPCTL
PA[1:0]	UART0	0	0	0	0	0x1
PA[5:2]	SSI0	0	0	0	0	0x2
PB[3:2]	I ² C0	0	0	0	0	0x3
PC[3:0]	JTAG/SWD	1	1	0	1	0x1

The GPIO commit control registers provide a layer of protection against accidental programming of critical hardware signals including the GPIO pins that can function as JTAG/SWD signals and the NMI signal. The commit control process must be followed for these pins, even if they are programmed as alternate functions other than JTAG/SWD or NMI, see "Commit Control" on page 654.

Table 10-2. GPIO Pins and Alternate Functions (100LQFP)

Ю	Pin	Analog Function	Digital Function (GPIOPCTL PMCx Bit Field Encoding) ^a											
			1	2	3	4	5	6	7	8	9	14	15	
PA0	26	-	U0Rx	-	-	-	-	-	-	CAN1Rx	-	-	-	
PA1	27	-	U0Tx	-	-	-	-	-	-	CAN1Tx	-	-	-	
PA2	28	-	-	SSI0Clk	-	-	-	-	-	-	-	-	-	
PA3	29	-	-	SSI0Fss	-	-	-	-	-	-	-	-	-	
PA4	30	-	-	SSI0Rx	-	-	-	-	-	-	-	-	-	
PA5	31	-	-	SSIOTx	-	-	-	-	-	-	-	-	-	
PA6	34	-	-	-	I2C1SCL	-	M1PWM2	-	-	-	-	-	-	
PA7	35	-	-	-	I2C1SDA	-	м1рwм3	-	-	-	-	-	-	
PB0	70	USB0ID	U1Rx	-	-	-	-	-	T2CCP0	-	-	-	-	
PB1	71	USB0VBUS	U1Tx	-	-	-	-	-	T2CCP1	-	-	-	-	
PB2	72	-	-	-	I2C0SCL	-	-	-	T3CCP0	-	-	-	-	
PB3	73	-	-	-	I2C0SDA	-	-	-	T3CCP1	-	-	-	-	
PB4	92	AIN10	-	SSI2Clk	-	M0PWM2	-	-	T1CCP0	CAN0Rx	-	-	-	
PB5	91	AIN11	-	SSI2Fss	-	моримз	-	-	T1CCP1	CAN0Tx	-	-	-	
PC0	85	-	TCK SWCLK	-	-	-	-	-	T4CCP0	-	-	-	-	
PC1	84	-	TMS SWDIO	-	-	-	-	-	T4CCP1	-	-	-	-	

Table 10-2. GPIO Pins and Alternate Functions (100LQFP) (continued)

Ю	Pin	Analog	Digital Function (GPIOPCTL PMCx Bit Field Encoding) ^a											
		Function	1	2	3	4	5	6	7	8	9	14	15	
PC2	83	-	TDI	-	-	-	-	-	T5CCP0	-	-	-	-	
PC3	82	-	TDO SWO	-	-	-	-	-	T5CCP1	-	-	-	-	
PC4	25	C1-	U4Rx	U1Rx	-	морwм6	-	IDX1	WT0CCP0	U1RTS	-	-	-	
PC5	24	C1+	U4Tx	U1Tx	-	морwм7	-	PhA1	WT0CCP1	U1CTS	-	-	-	
PC6	23	C0+	U3Rx	-	-	-	-	PhB1	WT1CCP0	USB0EPEN	-	-	-	
PC7	22	C0-	U3Tx	-	-	-	-	-	WT1CCP1	USB0PFLT	-	-	-	
PD0	1	AIN15	SSI3Clk	SSI1Clk	I2C3SCL	морwм6	M1PWM0	-	WT2CCP0	-	-	-	-	
PD1	2	AIN14	SSI3Fss	SSI1Fss	I2C3SDA	морwм7	M1PWM1	-	WT2CCP1	-	-	-	-	
PD2	3	AIN13	SSI3Rx	SSI1Rx	-	MOFAULTO	-	-	WT3CCP0	USB0EPEN	-	-	-	
PD3	4	AIN12	SSI3Tx	SSI1Tx	-	-	-	IDX0	WT3CCP1	USB0PFLT	-	-	-	
PD4	97	AIN7	U6Rx	-	-	-	-	-	WT4CCP0	-	-	-	-	
PD5	98	AIN6	U6Tx	-	-	-	-	-	WT4CCP1	-	-	-	-	
PD6	99	AIN5	U2Rx	-	-	MOFAULTO	-	PhA0	WT5CCP0	-	-	-	-	
PD7	100	AIN4	U2Tx	-	-	MOFAULT1	-	PhB0	WT5CCP1	NMI	-	-	-	
PE0	15	AIN3	U7Rx	-	-	-	-	-	-	-	-	-	-	
PE1	14	AIN2	U7Tx	-	-	-	-	-	-	-	-	-	-	
PE2	13	AIN1	-	-	-	-	-	-	-	-	-	-	-	
PE3	12	AIN0	-	-	-	-	-	-	-	-	-	-	-	
PE4	95	AIN9	U5Rx	-	I2C2SCL	морим4	M1PWM2	-	-	CAN0Rx	-	-	-	
PE5	96	AIN8	U5Tx	-	I2C2SDA	морим5	M1PWM3	-	-	CAN0Tx	-	-	-	
PE6	89	AIN21	-	-	-	-	-	-	-	CAN1Rx	-	-	-	
PE7	90	AIN20	U1RI	-	-	-	-	-	-	CAN1Tx	-	-	-	
PF0	40	-	Ulrts	SSI1Rx	CAN0Rx	-	M1PWM4	PhA0	T0CCP0	NMI	C00	TRD2	-	
PF1	41	-	Ulcts	SSI1Tx	-	-	м1рwм5	PhB0	T0CCP1	-	C1o	TRD1	-	
PF2	42	-	U1DCD	SSI1Clk	-	MOFAULTO	м1рwм6	-	T1CCP0	-	C20	TRD0	-	
PF3	43	-	Uldsr	SSI1Fss	CAN0Tx	MOFAULT1	м1рwм7	-	T1CCP1	-	-	TRCLK	-	
PF4	39	-	U1DTR	-	-	MOFAULT2	M1FAULTO	IDX0	T2CCP0	USB0EPEN	-	TRD3	-	
PF5	37	-	-	-	-	MOFAULT3	-	-	T2CCP1	USB0PFLT	-	-	-	
PF6	36	-	-	-	I2C2SCL	-	-	-	T3CCP0	-	-	-	-	
PF7	58	-	-	-	I2C2SDA	-	M1FAULTO	-	T3CCP1	-	-	-	-	
PG0	62	-	-	-	I2C3SCL	-	M1FAULT1	PhA1	T4CCP0	-	-	-	-	
PG1	61	-	-	-	I2C3SDA	-	M1FAULT2	PhB1	T4CCP1	-	-	-	-	
PG2	60	-	-	-	I2C4SCL	MOFAULT1	M1PWM0	-	T5CCP0	-	-	-	-	
PG3	59	-	-	-	I2C4SDA	M0FAULT2	M1PWM1	PhA1	T5CCP1	-	-	-	-	
PG4	74	-	U2Rx	-	I2C1SCL	морим4	M1PWM2	PhB1	WT0CCP0	USB0EPEN	-	-	-	
PG5	75	-	U2Tx	-	I2C1SDA	морим5	M1PWM3	IDX1	WT0CCP1	USB0PFLT	-	-	-	
PG6	87	C2+	-	-	I2C5SCL	морим6	-	-	WT1CCP0	-	-	-	-	
PG7	88	C2-	-	-	I2C5SDA	морим7	IDX1	-	WT1CCP1	-	-	-	-	
PH0	16	AIN16	-	SSI3Clk	-	моримо	-	MOFAULTO	WT2CCP0	-	-	-	-	

Table 10-2. GPIO Pins and Alternate Functions (100LQFP) (continued)


10	Pin	Analog			Dig	igital Function (GPIOPCTL PMCx Bit Field Encoding) ^a							
10	Pin	Function	1	2	3	4	5	6	7	8	9	14	15
PH1	17	AIN17	-	SSI3Fss	-	M0PWM1	IDX0	M0FAULT1	WT2CCP1	-	-	-	-
PH2	18	AIN18	-	SSI3Rx	-	морим2	-	M0FAULT2	WT5CCP0	-	-	-	-
РН3	19	AIN19	-	SSI3Tx	-	морwмз	-	MOFAULT3	WT5CCP1	-	-	-	-
PH4	79	-	-	SSI2Clk	-	морим4	PhA0	-	WT3CCP0	-	-	-	-
PH5	78	-	-	SSI2Fss	-	морим5	PhB0	-	WT3CCP1	-	-	-	-
РН6	77	-	-	SSI2Rx	-	морим6	-	-	WT4CCP0	-	-	-	-
PH7	76	-	-	SSI2Tx	-	морим7	-	-	WT4CCP1	-	-	-	-
рј0	68	USB0DM	U4Rx	-	-	-	-	-	T1CCP0	-	-	-	-
PJ1	69	USB0DP	U4Tx	-	-	-	-	-	T1CCP1	-	-	-	-
PJ2	11	-	U5Rx	-	-	-	IDX0	-	T2CCP0	-	-	-	-
PK0	49	-	-	SSI3Clk	-	-	-	M1FAULT0	-	-	-	-	-
PK1	48	-	-	SSI3Fss	-	-	-	M1FAULT1	-	-	-	-	-
PK2	47	-	-	SSI3Rx	-	-	-	M1FAULT2	-	-	-	-	-
PK3	46	-	-	SSI3Tx	-	-	-	M1FAULT3	-	-	-	-	-

a. The digital signals that are shaded gray are the power-on default values for the corresponding GPIO pin. Encodings 10-13 are not used on this device.

10.2 Functional Description

Each GPIO port is a separate hardware instantiation of the same physical block (see Figure 10-1 on page 650 and Figure 10-2 on page 651). The LM4F232H5QC microcontroller contains ten ports and thus ten of these physical GPIO blocks. Note that not all pins are implemented on every block. Some GPIO pins can function as I/O signals for the on-chip peripheral modules. For information on which GPIO pins are used for alternate hardware functions, refer to Table 23-5 on page 1367.

Figure 10-1. Digital I/O Pads






Figure 10-2. Analog/Digital I/O Pads

10.2.1 Data Control

The data control registers allow software to configure the operational modes of the GPIOs. The data direction register configures the GPIO as an input or an output while the data register either captures incoming data or drives it out to the pads.

Caution – It is possible to create a software sequence that prevents the debugger from connecting to the Stellaris® microcontroller. If the program code loaded into flash immediately changes the JTAG pins to their GPIO functionality, the debugger may not have enough time to connect and halt the controller before the JTAG pin functionality switches. As a result, the debugger may be locked out of the part. This issue can be avoided with a software routine that restores JTAG functionality based on an external or software trigger. In the case that the software routine is not implemented and the device is locked out of the part, this issue can be solved by using the Stellaris Flash Programmer "Unlock" feature. Please refer to LMFLASHPROGRAMMER on the TI web for more information.

10.2.1.1 Data Direction Operation

The **GPIO Direction (GPIODIR)** register (see page 662) is used to configure each individual pin as an input or output. When the data direction bit is cleared, the GPIO is configured as an input, and the corresponding data register bit captures and stores the value on the GPIO port. When the data

direction bit is set, the GPIO is configured as an output, and the corresponding data register bit is driven out on the GPIO port.


10.2.1.2 Data Register Operation

To aid in the efficiency of software, the GPIO ports allow for the modification of individual bits in the **GPIO Data (GPIODATA)** register (see page 660) by using bits [9:2] of the address bus as a mask. In this manner, software drivers can modify individual GPIO pins in a single instruction without affecting the state of the other pins. This method is more efficient than the conventional method of performing a read-modify-write operation to set or clear an individual GPIO pin. To implement this feature, the **GPIODATA** register covers 256 locations in the memory map.

During a write, if the address bit associated with that data bit is set, the value of the **GPIODATA** register is altered. If the address bit is cleared, the data bit is left unchanged.


For example, writing a value of 0xEB to the address GPIODATA + 0x098 has the results shown in Figure 10-3, where ${\tt u}$ indicates that data is unchanged by the write. This example demonstrates how **GPIODATA** bits 5, 2, and 1 are written.

Figure 10-3. GPIODATA Write Example



During a read, if the address bit associated with the data bit is set, the value is read. If the address bit associated with the data bit is cleared, the data bit is read as a zero, regardless of its actual value. For example, reading address GPIODATA + 0x0C4 yields as shown in Figure 10-4. This example shows how to read **GPIODATA** bits 5, 4, and 0.

Figure 10-4. GPIODATA Read Example



10.2.2 Interrupt Control

The interrupt capabilities of each GPIO port are controlled by a set of seven registers. These registers are used to select the source of the interrupt, its polarity, and the edge properties. When one or more GPIO inputs cause an interrupt, a single interrupt output is sent to the interrupt controller for the entire GPIO port. For edge-triggered interrupts, software must clear the interrupt to enable any

further interrupts. For a level-sensitive interrupt, the external source must hold the level constant for the interrupt to be recognized by the controller.

Three registers define the edge or sense that causes interrupts:

- GPIO Interrupt Sense (GPIOIS) register (see page 663)
- GPIO Interrupt Both Edges (GPIOIBE) register (see page 664)
- GPIO Interrupt Event (GPIOIEV) register (see page 665)

Interrupts are enabled/disabled via the GPIO Interrupt Mask (GPIOIM) register (see page 666).

When an interrupt condition occurs, the state of the interrupt signal can be viewed in two locations: the **GPIO Raw Interrupt Status (GPIORIS)** and **GPIO Masked Interrupt Status (GPIOMIS)** registers (see page 667 and page 668). As the name implies, the **GPIOMIS** register only shows interrupt conditions that are allowed to be passed to the interrupt controller. The **GPIORIS** register indicates that a GPIO pin meets the conditions for an interrupt, but has not necessarily been sent to the interrupt controller.

For a GPIO level-detect interrupt, the interrupt signal generating the interrupt must be held until serviced. Once the input signal deasserts from the interrupt generating logical sense, the corresponding RIS bit in the **GPIORIS** register clears. For a GPIO edge-detect interrupt, the RIS bit in the **GPIORIS** register is cleared by writing a '1' to the corresponding bit in the **GPIO Interrupt Clear (GPIOICR)** register (see page 669). The corresponding **GPIOMIS** bit reflects the masked value of the RIS bit.

When programming the interrupt control registers (**GPIOIS**, **GPIOIBE**, or **GPIOIEV**), the interrupts should be masked (**GPIOIM** cleared). Writing any value to an interrupt control register can generate a spurious interrupt if the corresponding bits are enabled.

10.2.2.1 ADC Trigger Source

Any GPIO pin can be configured to be an external trigger for the ADC using the **GPIO ADC Control** (**GPIOADCCTL**) register. If any GPIO is configured as a non-masked interrupt pin (the appropriate bit of **GPIOIM** is set), and an interrupt for that port is generated, a trigger signal is sent to the ADC. If the **ADC Event Multiplexer Select (ADCEMUX)** register is configured to use the external trigger, an ADC conversion is initiated. See page 833.

Note that if the Port B **GPIOADCCTL** register is cleared, PB4 can still be used as an external trigger for the ADC. This is a legacy mode which allows code written for previous Stellaris devices to operate on this microcontroller.

10.2.2.2 µDMA Trigger Source

Any GPIO pin can be configured to be an external trigger for the μ DMA using the **GPIO DMA Control (GPIODMACTL)** register. If any GPIO is configured as a non-masked interrupt pin (the appropriate bit of **GPIOIM** is set), an interrupt for that port is generated and an external trigger signal is sent to the μ DMA. If the μ DMA is configured to start a transfer based on the GPIO signal, a transfer is initiated.

10.2.3 Mode Control

The GPIO pins can be controlled by either software or hardware. Software control is the default for most signals and corresponds to the GPIO mode, where the **GPIODATA** register is used to read or write the corresponding pins. When hardware control is enabled via the **GPIO Alternate Function**

Select (GPIOAFSEL) register (see page 670), the pin state is controlled by its alternate function (that is, the peripheral).

Further pin muxing options are provided through the **GPIO Port Control (GPIOPCTL)** register which selects one of several peripheral functions for each GPIO. For information on the configuration options, refer to Table 23-5 on page 1367.

Note: If any pin is to be used as an ADC input, the appropriate bit in the **GPIOAMSEL** register must be set to disable the analog isolation circuit.

10.2.4 Commit Control

The GPIO commit control registers provide a layer of protection against accidental programming of critical hardware peripherals. Protection is provided for the GPIO pins that can be used as the four JTAG/SWD pins (PC[3:0]) and the NMI pin (PD7 and PF0). Writes to protected bits of the GPIO Alternate Function Select (GPIOAFSEL) register (see page 670), GPIO Pull Up Select (GPIOPUR) register (see page 676), GPIO Pull-Down Select (GPIOPDR) register (see page 678), and GPIO Digital Enable (GPIODEN) register (see page 681) are not committed to storage unless the GPIO Lock (GPIOLOCK) register (see page 683) has been unlocked and the appropriate bits of the GPIO Commit (GPIOCR) register (see page 684) have been set.

10.2.5 Pad Control

The pad control registers allow software to configure the GPIO pads based on the application requirements. The pad control registers include the **GPIODR2R**, **GPIODR4R**, **GPIODR8R**, **GPIODDR9**, **GPIODDR9**, **GPIODDR9**, **GPIODDR9**, and **GPIODDE9** registers. These registers control drive strength, open-drain configuration, pull-up and pull-down resistors, slew-rate control and digital input enable for each GPIO. If 5 V is applied to a GPIO configured as an open-drain output, the output voltage will depend on the strength of your pull-up resistor. The GPIO pad is not electrically configured to output 5 V.

10.2.6 Identification

The identification registers configured at reset allow software to detect and identify the module as a GPIO block. The identification registers include the **GPIOPeriphID0-GPIOPeriphID7** registers as well as the **GPIOPCeIIID0-GPIOPCeIIID3** registers.

10.3 Initialization and Configuration

The GPIO modules may be accessed via two different memory apertures. The legacy aperture, the Advanced Peripheral Bus (APB), is backwards-compatible with previous Stellaris parts. The other aperture, the Advanced High-Performance Bus (AHB), offers the same register map but provides better back-to-back access performance than the APB bus. These apertures are mutually exclusive. The aperture enabled for a given GPIO port is controlled by the appropriate bit in the **GPIOHBCTL** register (see page 260). Note that GPIO port K can only be accessed through the AHB aperture.

To configure the GPIO pins of a particular port, follow these steps:

- Enable the clock to the port by setting the appropriate bits in the RCGCGPIO register (see page 330). In addition, the SCGCGPIO and DCGCGPIO registers can be programmed in the same manner to enable clocking in Sleep and Deep-sleep modes.
- 2. Set the direction of the GPIO port pins by programming the **GPIODIR** register. A write of a '1' indicates output and a write of a '0' indicates input.

- 3. Configure the **GPIOAFSEL** register to program each bit as a GPIO or alternate pin. If an alternate pin is chosen for a bit, then the PMCx field must be programmed in the **GPIOPCTL** register for the specific peripheral required. There are also two registers, **GPIOADCCTL** and **GPIODMACTL**, which can be used to program a GPIO pin as a ADC or μDMA trigger, respectively.
- **4.** Set the drive strength for each of the pins through the **GPIODR2R**, **GPIODR4R**, and **GPIODR8R** registers.
- **5.** Program each pad in the port to have either pull-up, pull-down, or open drain functionality through the **GPIOPUR**, **GPIOPDR**, **GPIOODR** register. Slew rate may also be programmed, if needed, through the **GPIOSLR** register.
- **6.** To enable GPIO pins as digital I/Os, set the appropriate DEN bit in the **GPIODEN** register. To enable GPIO pins to their analog function (if available), set the GPIOAMSEL bit in the **GPIOAMSEL** register.
- **7.** Program the **GPIOIS**, **GPIOIBE**, **GPIOBE**, **GPIOEV**, and **GPIOIM** registers to configure the type, event, and mask of the interrupts for each port.
- **8.** Optionally, software can lock the configurations of the NMI and JTAG/SWD pins on the GPIO port pins, by setting the LOCK bits in the **GPIOLOCK** register.

When the internal POR signal is asserted and until otherwise configured, all GPIO pins are configured to be undriven (tristate): **GPIOAFSEL=0**, **GPIODEN=0**, **GPIOPDR=0**, and **GPIOPUR=0**, except for the pins shown in Table 10-1 on page 647. Table 10-3 on page 655 shows all possible configurations of the GPIO pads and the control register settings required to achieve them. Table 10-4 on page 656 shows how a rising edge interrupt is configured for pin 2 of a GPIO port.

Table 10-3. GPIO Pad Configuration Examples

Configuration	GPIO Reg	GPIO Register Bit Value ^a												
Configuration	AFSEL	DIR	ODR	DEN	PUR	PDR	DR2R	DR4R	DR8R	SLR				
Digital Input (GPIO)	0	0	0	1	?	?	Х	Х	Х	Х				
Digital Output (GPIO)	0	1	0	1	?	?	?	?	?	?				
Open Drain Output (GPIO)	0	1	1	1	Х	Х	?	?	?	?				
Open Drain Input/Output (I2CSDA)	1	Х	1	1	Х	Х	?	?	?	?				
Digital Input (Timer CCP)	1	Х	0	1	?	?	Х	Х	Х	Х				
Digital Input (QEI)	1	Х	0	1	?	?	Х	Х	Х	Х				
Digital Output (PWM)	1	Х	0	1	?	?	?	?	?	?				
Digital Output (Timer PWM)	1	Х	0	1	?	?	?	?	?	?				
Digital Input/Output (SSI)	1	Х	0	1	?	?	?	?	?	?				
Digital Input/Output (UART)	1	Х	0	1	?	?	?	?	?	?				
Analog Input (Comparator)	0	0	0	0	0	0	Х	Х	X	Х				

Table 10-3. GPIO Pad Configuration Examples (continued)

Configuration	GPIO Reg	GPIO Register Bit Value ^a										
Comiguration	AFSEL	DIR	ODR	DEN	PUR	PDR	DR2R	DR4R	DR8R	SLR		
Digital Output (Comparator)	1	Х	0	1	?	?	?	?	?	?		

a. X=Ignored (don't care bit)

Table 10-4. GPIO Interrupt Configuration Example

Register	Desired Interrupt	Pin 2 Bit Value ^a								
Register	Event Trigger	7	6	5	4	3	2	1	0	
GPIOIS	0=edge	Х	Х	Х	Х	Х	0	Х	Х	
	1=level									
GPIOIBE	0=single edge	Х	Х	Х	Х	Х	0	Х	Х	
	1=both edges									
GPIOIEV	0=Low level, or falling edge	Х	Х	Х	Х	Х	1	Х	Х	
	1=High level, or rising edge									
GPIOIM	0=masked	0	0	0	0	0	1	0	0	
	1=not masked									

a. X=Ignored (don't care bit)

10.4 Register Map

Table 10-6 on page 657 lists the GPIO registers. Each GPIO port can be accessed through one of two bus apertures. The legacy aperture, the Advanced Peripheral Bus (APB), is backwards-compatible with previous Stellaris parts. The other aperture, the Advanced High-Performance Bus (AHB), offers the same register map but provides better back-to-back access performance than the APB bus.

Important: The GPIO registers in this chapter are duplicated in each GPIO block; however, depending on the block, all eight bits may not be connected to a GPIO pad. In those cases, writing to unconnected bits has no effect, and reading unconnected bits returns no meaningful data.

The offset listed is a hexadecimal increment to the register's address, relative to that GPIO port's base address:

- GPIO Port A (APB): 0x4000.4000
- GPIO Port A (AHB): 0x4005.8000
- GPIO Port B (APB): 0x4000.5000
- GPIO Port B (AHB): 0x4005.9000
- GPIO Port C (APB): 0x4000.6000
- GPIO Port C (AHB): 0x4005.A000
- GPIO Port D (APB): 0x4000.7000
- GPIO Port D (AHB): 0x4005.B000
- GPIO Port E (APB): 0x4002.4000
- GPIO Port E (AHB): 0x4005.C000
- GPIO Port F (APB): 0x4002.5000
- GPIO Port F (AHB): 0x4005.D000

^{?=}Can be either 0 or 1, depending on the configuration

- GPIO Port G (APB): 0x4002.6000
- GPIO Port G (AHB): 0x4005.E000
- GPIO Port H (APB): 0x4002.7000
- GPIO Port H (AHB): 0x4005.F000
- GPIO Port J (APB): 0x4003.D000
- GPIO Port J (AHB): 0x4006.0000
- GPIO Port K (AHB): 0x4006.1000

Note that each GPIO module clock must be enabled before the registers can be programmed (see page 330). There must be a delay of 3 system clocks after the GPIO module clock is enabled before any GPIO module registers are accessed.

Important: All GPIO pins are configured as GPIOs and tri-stated by default (GPIOAFSEL=0, GPIODEN=0, GPIOPDR=0, GPIOPUR=0, and GPIOPCTL=0), with the exception of the pins shown in the table below. A Power-On-Reset (POR) or asserting RST puts the pins back to their default state.

Table 10-5. GPIO Pins With Non-Zero Reset Values

GPIO Pins	Default State	GPIOAFSEL	GPIODEN	GPIOPDR	GPIOPUR	GPIOPCTL
PA[1:0]	UART0	0	0	0	0	0x1
PA[5:2]	SSI0	0	0	0	0	0x2
PB[3:2]	I ² C0	0	0	0	0	0x3
PC[3:0]	JTAG/SWD	1	1	0	1	0x1

The GPIO commit control registers provide a layer of protection against accidental programming of critical hardware signals including the GPIO pins that can function as JTAG/SWD signals and the NMI signal. The commit control process must be followed for these pins, even if they are programmed as alternate functions other than JTAG/SWD or NMI, see "Commit Control" on page 654.

The default register type for the **GPIOCR** register is RO for all GPIO pins with the exception of the NMI pin and the four JTAG/SWD pins (PD7, PF0, and PC[3:0]). These six pins are the only GPIOs that are protected by the **GPIOCR** register. Because of this, the register type for GPIO Port D7, GPIO Port F0, and GPIO Port C[3:0] is R/W.

The default reset value for the **GPIOCR** register is 0x0000.00FF for all GPIO pins, with the exception of the NMI pin and the four JTAG/SWD pins (PD7, PF0, and PC[3:0]). To ensure that the JTAG port is not accidentally programmed as GPIO pins, the PC[3:0] pins default to non-committable. Similarly, to ensure that the NMI pin is not accidentally programmed as a GPIO pin, the PD7 and PF0 pins default to non-committable. Because of this, the default reset value of **GPIOCR** for GPIO Port C is 0x0000.00F0, for GPIO Port D is 0x0000.00FF, and for GPIO Port F is 0x0000.00FE.

Table 10-6. GPIO Register Map

Offset	Name	Туре	Reset	Description	See page
0x000	GPIODATA	R/W	0x0000.0000	GPIO Data	660
0x400	GPIODIR	R/W	0x0000.0000	GPIO Direction	662
0x404	GPIOIS	R/W	0x0000.0000	GPIO Interrupt Sense	663
0x408	GPIOIBE	R/W	0x0000.0000	GPIO Interrupt Both Edges	664

Table 10-6. GPIO Register Map (continued)

Offset	Name	Туре	Reset	Description	See page
0x40C	GPIOIEV	R/W	0x0000.0000	GPIO Interrupt Event	665
0x410	GPIOIM	R/W	0x0000.0000	GPIO Interrupt Mask	666
0x414 GPIORIS		RO	0x0000.0000	GPIO Raw Interrupt Status	667
0x418	GPIOMIS	RO	0x0000.0000	GPIO Masked Interrupt Status	668
0x41C	GPIOICR	W1C	0x0000.0000	GPIO Interrupt Clear	669
0x420	GPIOAFSEL	R/W	-	GPIO Alternate Function Select	670
0x500	GPIODR2R	R/W	0x0000.00FF	GPIO 2-mA Drive Select	672
0x504	GPIODR4R	R/W	0x0000.0000	GPIO 4-mA Drive Select	673
0x508	GPIODR8R	R/W	0x0000.0000	GPIO 8-mA Drive Select	674
0x50C	GPIOODR	R/W	0x0000.0000	GPIO Open Drain Select	675
0x510	GPIOPUR	R/W	-	GPIO Pull-Up Select	676
0x514	GPIOPDR	R/W	0x0000.0000	GPIO Pull-Down Select	678
0x518	GPIOSLR	R/W	0x0000.0000	GPIO Slew Rate Control Select	680
0x51C	GPIODEN	R/W	-	GPIO Digital Enable	681
0x520	GPIOLOCK	R/W	0x0000.0001	GPIO Lock	683
0x524	GPIOCR	-	-	GPIO Commit	684
0x528	GPIOAMSEL	R/W	0x0000.0000	GPIO Analog Mode Select	686
0x52C	GPIOPCTL	R/W	-	GPIO Port Control	688
0x530	GPIOADCCTL	R/W	0x0000.0000	GPIO ADC Control	690
0x534	GPIODMACTL	R/W	0x0000.0000	GPIO DMA Control	691
0xFD0	GPIOPeriphID4	RO	0x0000.0000	GPIO Peripheral Identification 4	692
0xFD4	GPIOPeriphID5	RO	0x0000.0000	GPIO Peripheral Identification 5	693
0xFD8	GPIOPeriphID6	RO	0x0000.0000	GPIO Peripheral Identification 6	694
0xFDC	GPIOPeriphID7	RO	0x0000.0000	GPIO Peripheral Identification 7	695
0xFE0	GPIOPeriphID0	RO	0x0000.0061	GPIO Peripheral Identification 0	696
0xFE4	GPIOPeriphID1	RO	0x0000.0000	GPIO Peripheral Identification 1	697
0xFE8	GPIOPeriphID2	RO	0x0000.0018	GPIO Peripheral Identification 2	698
0xFEC	GPIOPeriphID3	RO	0x0000.0001	GPIO Peripheral Identification 3	699
0xFF0	GPIOPCellID0	RO	0x0000.000D	GPIO PrimeCell Identification 0	700
0xFF4	GPIOPCellID1	RO	0x0000.00F0	GPIO PrimeCell Identification 1	701
0xFF8	GPIOPCellID2	RO	0x0000.0005	GPIO PrimeCell Identification 2	702
0xFFC	GPIOPCellID3	RO	0x0000.00B1	GPIO PrimeCell Identification 3	703

10.5 Register Descriptions

The remainder of this section lists and describes the GPIO registers, in numerical order by address offset.

Register 1: GPIO Data (GPIODATA), offset 0x000

The **GPIODATA** register is the data register. In software control mode, values written in the **GPIODATA** register are transferred onto the GPIO port pins if the respective pins have been configured as outputs through the **GPIO Direction (GPIODIR)** register (see page 662).


In order to write to **GPIODATA**, the corresponding bits in the mask, resulting from the address bus bits [9:2], must be set. Otherwise, the bit values remain unchanged by the write.

Similarly, the values read from this register are determined for each bit by the mask bit derived from the address used to access the data register, bits [9:2]. Bits that are set in the address mask cause the corresponding bits in **GPIODATA** to be read, and bits that are clear in the address mask cause the corresponding bits in **GPIODATA** to be read as 0, regardless of their value.

A read from **GPIODATA** returns the last bit value written if the respective pins are configured as outputs, or it returns the value on the corresponding input pin when these are configured as inputs. All bits are cleared by a reset.

GPIO Data (GPIODATA)

GPIO Port A (APB) base: 0x4000.4000 GPIO Port A (AHB) base: 0x4005.8000 GPIO Port B (APB) base: 0x4000.5000 GPIO Port B (AHB) base: 0x4005.9000 GPIO Port C (APB) base: 0x4000.6000 GPIO Port C (AHB) base: 0x4005.A000 GPIO Port D (APB) base: 0x4000,7000 GPIO Port D (AHB) base: 0x4005.B000 GPIO Port E (APB) base: 0x4002.4000 GPIO Port E (AHB) base: 0x4005.C000 GPIO Port F (APB) base: 0x4002.5000 GPIO Port F (AHB) base: 0x4005.D000 GPIO Port G (APB) base: 0x4002.6000 GPIO Port G (AHB) base: 0x4005.E000 GPIO Port H (APB) base: 0x4002.7000 GPIO Port H (AHB) base: 0x4005.F000 GPIO Port J (APB) base: 0x4003.D000 GPIO Port J (AHB) base: 0x4006.0000 GPIO Port K (AHB) base: 0x4006.1000 Offset 0x000



Bit/Field Name Type Reset Description

31:8 reserved RO 0x0000.00 Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.

Bit/Field	Name	Type	Reset	Description
7:0	DATA	R/W	0x00	GPIO Data


This register is virtually mapped to 256 locations in the address space. To facilitate the reading and writing of data to these registers by independent drivers, the data read from and written to the registers are masked by the eight address lines [9:2]. Reads from this register return its current state. Writes to this register only affect bits that are not masked by ADDR[9:2] and are configured as outputs. See "Data Register Operation" on page 652 for examples of reads and writes.

Register 2: GPIO Direction (GPIODIR), offset 0x400

The **GPIODIR** register is the data direction register. Setting a bit in the **GPIODIR** register configures the corresponding pin to be an output, while clearing a bit configures the corresponding pin to be an input. All bits are cleared by a reset, meaning all GPIO pins are inputs by default.

GPIO Direction (GPIODIR)

GPIO Port A (APB) base: 0x4000.4000 GPIO Port A (AHB) base: 0x4005.8000 GPIO Port B (APB) base: 0x4000.5000 GPIO Port B (AHB) base: 0x4005.9000 GPIO Port C (APB) base: 0x4000.6000 GPIO Port C (AHB) base: 0x4005.A000 GPIO Port D (APB) base: 0x4000.7000 GPIO Port D (AHB) base: 0x4005.B000 GPIO Port E (APB) base: 0x4002.4000 GPIO Port E (AHB) base: 0x4005.C000 GPIO Port F (APB) base: 0x4002.5000 GPIO Port F (AHB) base: 0x4005.D000 GPIO Port G (APB) base: 0x4002.6000 GPIO Port G (AHB) base: 0x4005.E000 GPIO Port H (APB) base: 0x4002.7000 GPIO Port H (AHB) base: 0x4005.F000 GPIO Port J (APB) base: 0x4003.D000 GPIO Port J (AHB) base: 0x4006.0000 GPIO Port K (AHB) base: 0x4006.1000 Offset 0x400



Bit/Field	Name	Type	Reset	Description
31:8	reserved	RO	0x0000.00	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
7:0	DIR	R/W	0x00	GPIO Data Direction


- 0 Corresponding pin is an input.
- 1 Corresponding pins is an output.


Register 3: GPIO Interrupt Sense (GPIOIS), offset 0x404

The **GPIOIS** register is the interrupt sense register. Setting a bit in the **GPIOIS** register configures the corresponding pin to detect levels, while clearing a bit configures the corresponding pin to detect edges. All bits are cleared by a reset.

GPIO Interrupt Sense (GPIOIS)

GPIO Port A (APB) base: 0x4000.4000 GPIO Port A (AHB) base: 0x4005.8000 GPIO Port B (APB) base: 0x4000.5000 GPIO Port B (AHB) base: 0x4005.9000 GPIO Port C (APB) base: 0x4000.6000 GPIO Port C (AHB) base: 0x4005.A000 GPIO Port D (APB) base: 0x4000.7000 GPIO Port D (AHB) base: 0x4005.B000 GPIO Port E (APB) base: 0x4002.4000 GPIO Port E (AHB) base: 0x4005.C000 GPIO Port F (APB) base: 0x4002.5000 GPIO Port F (AHB) base: 0x4005.D000 GPIO Port G (APB) base: 0x4002.6000 GPIO Port G (AHB) base: 0x4005.E000 GPIO Port H (APB) base: 0x4002.7000 GPIO Port H (AHB) base: 0x4005.F000 GPIO Port J (APB) base: 0x4003.D000 GPIO Port J (AHB) base: 0x4006.0000 GPIO Port K (AHB) base: 0x4006.1000 Offset 0x404





Bit/Field	Name	Type	Reset	Description
31:8	reserved	RO	0x0000.00	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
7:0	IS	R/W	0x00	GPIO Interrupt Sense

- The edge on the corresponding pin is detected (edge-sensitive).
- 1 The level on the corresponding pin is detected (level-sensitive).


Register 4: GPIO Interrupt Both Edges (GPIOIBE), offset 0x408

The **GPIOIBE** register allows both edges to cause interrupts. When the corresponding bit in the **GPIO Interrupt Sense (GPIOIS)** register (see page 663) is set to detect edges, setting a bit in the **GPIOIBE** register configures the corresponding pin to detect both rising and falling edges, regardless of the corresponding bit in the **GPIO Interrupt Event (GPIOIEV)** register (see page 665). Clearing a bit configures the pin to be controlled by the **GPIOIEV** register. All bits are cleared by a reset.

GPIO Interrupt Both Edges (GPIOIBE)

GPIO Port A (APB) base: 0x4000.4000 GPIO Port A (AHB) base: 0x4005.8000 GPIO Port B (APB) base: 0x4000.5000 GPIO Port B (AHB) base: 0x4005.9000 GPIO Port C (APB) base: 0x4000.6000 GPIO Port C (AHB) base: 0x4005.A000 GPIO Port D (APB) base: 0x4000.7000 GPIO Port D (AHB) base: 0x4005.B000 GPIO Port E (APB) base: 0x4002.4000 GPIO Port E (AHB) base: 0x4005.C000 GPIO Port F (APB) base: 0x4002.5000 GPIO Port F (AHB) base: 0x4005.D000 GPIO Port G (APB) base: 0x4002.6000 GPIO Port G (AHB) base: 0x4005.E000 GPIO Port H (APB) base: 0x4002.7000 GPIO Port H (AHB) base: 0x4005.F000 GPIO Port J (APB) base: 0x4003.D000 GPIO Port J (AHB) base: 0x4006.0000 GPIO Port K (AHB) base: 0x4006.1000 Offset 0x408 Type R/W, reset 0x0000.0000

D:4/E: -1-4



Divrieiu	iname	туре	Reset	Description
31:8	reserved	RO	0x0000.00	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
7:0	IBE	R/W	0x00	GPIO Interrupt Both Edges

Dogorintion

- 0 Interrupt generation is controlled by the GPIO Interrupt Event (GPIOIEV) register (see page 665).
- 1 Both edges on the corresponding pin trigger an interrupt.


Register 5: GPIO Interrupt Event (GPIOIEV), offset 0x40C

The **GPIOIEV** register is the interrupt event register. Setting a bit in the **GPIOIEV** register configures the corresponding pin to detect rising edges or high levels, depending on the corresponding bit value in the **GPIO Interrupt Sense (GPIOIS)** register (see page 663). Clearing a bit configures the pin to detect falling edges or low levels, depending on the corresponding bit value in the **GPIOIS** register. All bits are cleared by a reset.

GPIO Interrupt Event (GPIOIEV)

GPIO Port A (APB) base: 0x4000.4000 GPIO Port A (AHB) base: 0x4005.8000 GPIO Port B (APB) base: 0x4000.5000 GPIO Port B (AHB) base: 0x4005.9000 GPIO Port C (APB) base: 0x4000.6000 GPIO Port C (AHB) base: 0x4005.A000 GPIO Port D (APB) base: 0x4000.7000 GPIO Port D (AHB) base: 0x4005.B000 GPIO Port E (APB) base: 0x4002.4000 GPIO Port E (AHB) base: 0x4005.C000 GPIO Port F (APB) base: 0x4002.5000 GPIO Port F (AHB) base: 0x4005.D000 GPIO Port G (APB) base: 0x4002.6000 GPIO Port G (AHB) base: 0x4005.E000 GPIO Port H (APB) base: 0x4002.7000 GPIO Port H (AHB) base: 0x4005.F000 GPIO Port J (APB) base: 0x4003.D000 GPIO Port J (AHB) base: 0x4006.0000 GPIO Port K (AHB) base: 0x4006.1000 Offset 0x40C

D:4/E: -1-4



Divrieiu	Name	Type	Reset	Description
31:8	reserved	RO	0x0000.00	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
7:0	IEV	R/W	0x00	GPIO Interrupt Event

Dogorintion

- O A falling edge or a Low level on the corresponding pin triggers an interrupt.
- 1 A rising edge or a High level on the corresponding pin triggers an interrupt.


Register 6: GPIO Interrupt Mask (GPIOIM), offset 0x410

The **GPIOIM** register is the interrupt mask register. Setting a bit in the **GPIOIM** register allows interrupts that are generated by the corresponding pin to be sent to the interrupt controller on the combined interrupt signal. Clearing a bit prevents an interrupt on the corresponding pin from being sent to the interrupt controller. All bits are cleared by a reset.

GPIO Interrupt Mask (GPIOIM)

GPIO Port A (APB) base: 0x4000.4000 GPIO Port A (AHB) base: 0x4005.8000 GPIO Port B (APB) base: 0x4000.5000 GPIO Port B (AHB) base: 0x4005.9000 GPIO Port C (APB) base: 0x4000.6000 GPIO Port C (AHB) base: 0x4005.A000 GPIO Port D (APB) base: 0x4000.7000 GPIO Port D (AHB) base: 0x4005.B000 GPIO Port E (APB) base: 0x4002.4000 GPIO Port E (AHB) base: 0x4005.C000 GPIO Port F (APB) base: 0x4002.5000 GPIO Port F (AHB) base: 0x4005.D000 GPIO Port G (APB) base: 0x4002.6000 GPIO Port G (AHB) base: 0x4005.E000 GPIO Port H (APB) base: 0x4002.7000 GPIO Port H (AHB) base: 0x4005.F000 GPIO Port J (APB) base: 0x4003.D000 GPIO Port J (AHB) base: 0x4006.0000 GPIO Port K (AHB) base: 0x4006.1000 Offset 0x410

Type R/W, reset 0x0000.0000



Bit/Field	Name	Type	Reset	Description
31:8	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
7:0	IME	R/W	0x00	GPIO Interrupt Mask Enable

- 0 The interrupt from the corresponding pin is masked.
- The interrupt from the corresponding pin is sent to the interrupt controller.


Register 7: GPIO Raw Interrupt Status (GPIORIS), offset 0x414

The **GPIORIS** register is the raw interrupt status register. A bit in this register is set when an interrupt condition occurs on the corresponding GPIO pin. If the corresponding bit in the **GPIO Interrupt Mask (GPIOIM)** register (see page 666) is set, the interrupt is sent to the interrupt controller. Bits read as zero indicate that corresponding input pins have not initiated an interrupt. For a GPIO level-detect interrupt, the interrupt signal generating the interrupt must be held until serviced. Once the input signal deasserts from the interrupt generating logical sense, the corresponding RIS bit in the **GPIORIS** register clears. For a GPIO edge-detect interrupt, the RIS bit in the **GPIORIS** register is cleared by writing a '1' to the corresponding bit in the **GPIO Interrupt Clear (GPIOICR)** register. The corresponding **GPIOMIS** bit reflects the masked value of the RIS bit.

GPIO Raw Interrupt Status (GPIORIS)

GPIO Port A (APB) base: 0x4000.4000 GPIO Port A (AHB) base: 0x4005.8000 GPIO Port B (APB) base: 0x4000.5000 GPIO Port B (AHB) base: 0x4005.9000 GPIO Port C (APB) base: 0x4000.6000 GPIO Port C (AHB) base: 0x4005.A000 GPIO Port D (APB) base: 0x4000.7000 GPIO Port D (AHB) base: 0x4005.B000 GPIO Port E (APB) base: 0x4002.4000 GPIO Port E (AHB) base: 0x4005.C000 GPIO Port F (APB) base: 0x4002.5000 GPIO Port F (AHB) base: 0x4005.D000 GPIO Port G (APB) base: 0x4002.6000 GPIO Port G (AHB) base: 0x4005.E000 GPIO Port H (APB) base: 0x4002,7000 GPIO Port H (AHB) base: 0x4005.F000 GPIO Port J (APB) base: 0x4003.D000 GPIO Port J (AHB) base: 0x4006.0000 GPIO Port K (AHB) base: 0x4006.1000 Offset 0x414

Type RO, reset 0x0000.0000



Bit/Field	Name	Type	Reset	Description
31:8	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
7:0	RIS	RO	0x00	GPIO Interrupt Raw Status

Value Description

- O An interrupt condition has not occurred on the corresponding pin.
- 1 An interrupt condition has occurred on the corresponding pin.

For edge-detect interrupts, this bit is cleared by writing a 1 to the corresponding bit in the **GPIOICR** register.

For a GPIO level-detect interrupt, the bit is cleared when the level is deasserted.

Register 8: GPIO Masked Interrupt Status (GPIOMIS), offset 0x418


The **GPIOMIS** register is the masked interrupt status register. If a bit is set in this register, the corresponding interrupt has triggered an interrupt to the interrupt controller. If a bit is clear, either no interrupt has been generated, or the interrupt is masked.

Note that if the Port B **GPIOADCCTL** register is cleared, PB4 can still be used as an external trigger for the ADC. This is a legacy mode which allows code written for previous Stellaris devices to operate on this microcontroller.

GPIOMIS is the state of the interrupt after masking.

GPIO Masked Interrupt Status (GPIOMIS)

GPIO Port A (APB) base: 0x4000.4000 GPIO Port A (AHB) base: 0x4005.8000 GPIO Port B (APB) base: 0x4000.5000 GPIO Port B (AHB) base: 0x4005.9000 GPIO Port C (APB) base: 0x4000.6000 GPIO Port C (AHB) base: 0x4005.A000 GPIO Port D (APB) base: 0x4000.7000 GPIO Port D (AHB) base: 0x4005.B000 GPIO Port E (APB) base: 0x4002.4000 GPIO Port E (AHB) base: 0x4005.C000 GPIO Port F (APB) base: 0x4002.5000 GPIO Port F (AHB) base: 0x4005.D000 GPIO Port G (APB) base: 0x4002.6000 GPIO Port G (AHB) base: 0x4005.E000 GPIO Port H (APB) base: 0x4002.7000 GPIO Port H (AHB) base: 0x4005.F000 GPIO Port J (APB) base: 0x4003.D000 GPIO Port J (AHB) base: 0x4006.0000 GPIO Port K (AHB) base: 0x4006.1000 Offset 0x418



Bit/Field	Name	Type	Reset	Description
31:8	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
7:0	MIS	RO	0x00	GPIO Masked Interrupt Status

Value Description

- O An interrupt condition on the corresponding pin is masked or has not occurred.
- 1 An interrupt condition on the corresponding pin has triggered an interrupt to the interrupt controller.

For edge-detect interrupts, this bit is cleared by writing a 1 to the corresponding bit in the **GPIOICR** register.

For a GPIO level-detect interrupt, the bit is cleared when the level is deasserted.


Register 9: GPIO Interrupt Clear (GPIOICR), offset 0x41C

The **GPIOICR** register is the interrupt clear register. For edge-detect interrupts, writing a 1 to the IC bit in the **GPIOICR** register clears the corresponding bit in the **GPIORIS** and **GPIOMIS** registers. If the interrupt is a level-detect, the IC bit in this register has no effect. In addition, writing a 0 to any of the bits in the **GPIOICR** register has no effect.

GPIO Interrupt Clear (GPIOICR)

GPIO Port A (APB) base: 0x4000.4000 GPIO Port A (AHB) base: 0x4005.8000 GPIO Port B (APB) base: 0x4000.5000 GPIO Port B (AHB) base: 0x4005.9000 GPIO Port C (APB) base: 0x4000.6000 GPIO Port C (AHB) base: 0x4005.A000 GPIO Port D (APB) base: 0x4000.7000 GPIO Port D (AHB) base: 0x4005.B000 GPIO Port E (APB) base: 0x4002.4000 GPIO Port E (AHB) base: 0x4005.C000 GPIO Port F (APB) base: 0x4002.5000 GPIO Port F (AHB) base: 0x4005.D000 GPIO Port G (APB) base: 0x4002.6000 GPIO Port G (AHB) base: 0x4005.E000 GPIO Port H (APB) base: 0x4002.7000 GPIO Port H (AHB) base: 0x4005.F000 GPIO Port J (APB) base: 0x4003.D000 GPIO Port J (AHB) base: 0x4006.0000 GPIO Port K (AHB) base: 0x4006.1000 Offset 0x41C

Type W1C, reset 0x0000.0000



Bit/Field	Name	Type	Reset	Description
31:8	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
7:0	IC	W1C	0x00	GPIO Interrupt Clear

- 0 The corresponding interrupt is unaffected.
- 1 The corresponding interrupt is cleared.

Register 10: GPIO Alternate Function Select (GPIOAFSEL), offset 0x420

The **GPIOAFSEL** register is the mode control select register. If a bit is clear, the pin is used as a GPIO and is controlled by the GPIO registers. Setting a bit in this register configures the corresponding GPIO line to be controlled by an associated peripheral. Several possible peripheral functions are multiplexed on each GPIO. The **GPIO Port Control (GPIOPCTL)** register is used to select one of the possible functions. Table 23-5 on page 1367 details which functions are muxed on each GPIO pin. The reset value for this register is 0x0000.0000 for GPIO ports that are not listed in the table below.

Important: All GPIO pins are configured as GPIOs and tri-stated by default (GPIOAFSEL=0, GPIODEN=0, GPIOPDR=0, GPIOPUR=0, and GPIOPCTL=0), with the exception of the pins shown in the table below. A Power-On-Reset (POR) or asserting RST puts the pins back to their default state.

Table 10-7. GPIO Pins With Non-Zero Reset Values

GPIO Pins	Default State	GPIOAFSEL	GPIODEN	GPIOPDR	GPIOPUR	GPIOPCTL
PA[1:0]	UART0	0	0	0	0	0x1
PA[5:2]	SSI0	0	0	0	0	0x2
PB[3:2]	I ² C0	0	0	0	0	0x3
PC[3:0]	JTAG/SWD	1	1	0	1	0x1

The GPIO commit control registers provide a layer of protection against accidental programming of critical hardware signals including the GPIO pins that can function as JTAG/SWD signals and the NMI signal. The commit control process must be followed for these pins, even if they are programmed as alternate functions other than JTAG/SWD or NMI, see "Commit Control" on page 654.


Caution – It is possible to create a software sequence that prevents the debugger from connecting to the Stellaris microcontroller. If the program code loaded into flash immediately changes the JTAG pins to their GPIO functionality, the debugger may not have enough time to connect and halt the controller before the JTAG pin functionality switches. As a result, the debugger may be locked out of the part. This issue can be avoided with a software routine that restores JTAG functionality based on an external or software trigger. In the case that the software routine is not implemented and the device is locked out of the part, this issue can be solved by using the Stellaris Flash Programmer "Unlock" feature. Please refer to LMFLASHPROGRAMMER on the TI web for more information.

The GPIO commit control registers provide a layer of protection against accidental programming of critical hardware peripherals. Protection is provided for the GPIO pins that can be used as the four JTAG/SWD pins (PC[3:0]) and the NMI pin (PD7 and PF0). Writes to protected bits of the GPIO Alternate Function Select (GPIOAFSEL) register (see page 670), GPIO Pull Up Select (GPIOPUR) register (see page 676), GPIO Pull-Down Select (GPIOPDR) register (see page 678), and GPIO Digital Enable (GPIODEN) register (see page 681) are not committed to storage unless the GPIO Lock (GPIOLOCK) register (see page 683) has been unlocked and the appropriate bits of the GPIO Commit (GPIOCR) register (see page 684) have been set.

When using the I^2C module, in addition to setting the **GPIOAFSEL** register bits for the I^2C clock and data pins, the pins should be set to open drain using the **GPIO Open Drain Select (GPIOODR)** register (see examples in "Initialization and Configuration" on page 654).

GPIO Alternate Function Select (GPIOAFSEL)

GPIO Port A (APB) base: 0x4000.4000
GPIO Port A (AHB) base: 0x4005.8000
GPIO Port B (APB) base: 0x4005.8000
GPIO Port B (APB) base: 0x4005.9000
GPIO Port B (AHB) base: 0x4005.9000
GPIO Port C (APB) base: 0x4005.4000
GPIO Port C (APB) base: 0x4005.A000
GPIO Port D (APB) base: 0x4005.B000
GPIO Port D (APB) base: 0x4005.B000
GPIO Port E (APB) base: 0x4002.4000
GPIO Port E (APB) base: 0x4005.C000
GPIO Port E (APB) base: 0x4005.C000
GPIO Port F (APB) base: 0x4005.D000
GPIO Port G (APB) base: 0x4005.F000
GPIO Port G (APB) base: 0x4005.F000
GPIO Port H (APB) base: 0x4005.F000
GPIO Port J (APB) base: 0x4005.F000
GPIO Port J (APB) base: 0x4005.F000
GPIO Port J (APB) base: 0x4006.0000
GPIO Port J (AHB) base: 0x4006.1000
GPIO Port K (AHB) base: 0x4006.1000
Offset 0x420
Type R/W, reset -



Bit/Field	Name	Type	Reset	Description
31:8	reserved	RO	0x0000.00	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
7:0	ΔESEI	R/M	_	GPIO Alternate Function Select

Value Description

- The associated pin functions as a GPIO and is controlled by the GPIO registers.
- The associated pin functions as a peripheral signal and is controlled by the alternate hardware function.

The reset value for this register is 0x0000.0000 for GPIO ports that are not listed in Table 10-1 on page 647.


Register 11: GPIO 2-mA Drive Select (GPIODR2R), offset 0x500

The **GPIODR2R** register is the 2-mA drive control register. Each GPIO signal in the port can be individually configured without affecting the other pads. When setting the DRV2 bit for a GPIO signal, the corresponding DRV4 bit in the **GPIODR4R** register and DRV8 bit in the **GPIODR8R** register are automatically cleared by hardware. By default, all GPIO pins have 2-mA drive.

GPIO 2-mA Drive Select (GPIODR2R)

GPIO Port A (APB) base: 0x4000.4000 GPIO Port A (AHB) base: 0x4005.8000 GPIO Port B (APB) base: 0x4000.5000 GPIO Port B (AHB) base: 0x4005.9000 GPIO Port C (APB) base: 0x4000.6000 GPIO Port C (AHB) base: 0x4005.A000 GPIO Port D (APB) base: 0x4000.7000 GPIO Port D (AHB) base: 0x4005.B000 GPIO Port E (APB) base: 0x4002.4000 GPIO Port E (AHB) base: 0x4005.C000 GPIO Port F (APB) base: 0x4002.5000 GPIO Port F (AHB) base: 0x4005.D000 GPIO Port G (APB) base: 0x4002.6000 GPIO Port G (AHB) base: 0x4005.E000 GPIO Port H (APB) base: 0x4002.7000 GPIO Port H (AHB) base: 0x4005.F000 GPIO Port J (APB) base: 0x4003.D000 GPIO Port J (AHB) base: 0x4006.0000 GPIO Port K (AHB) base: 0x4006.1000 Offset 0x500

Type R/W, reset 0x0000.00FF



Bit/Field	Name	Type	Reset	Description
31:8	reserved	RO	0x0000.00	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
7:0	DRV2	R/W	0xFF	Output Pad 2-mA Drive Enable

Value Description

- The drive for the corresponding GPIO pin is controlled by the GPIODR4R or GPIODR8R register.
- 1 The corresponding GPIO pin has 2-mA drive.

Setting a bit in either the **GPIODR4** register or the **GPIODR8** register clears the corresponding 2-mA enable bit. The change is effective on the second clock cycle after the write if accessing GPIO via the APB memory aperture. If using AHB access, the change is effective on the next clock cycle.


Register 12: GPIO 4-mA Drive Select (GPIODR4R), offset 0x504

The GPIODR4R register is the 4-mA drive control register. Each GPIO signal in the port can be individually configured without affecting the other pads. When setting the DRV4 bit for a GPIO signal, the corresponding DRV2 bit in the GPIODR2R register and DRV8 bit in the GPIODR8R register are automatically cleared by hardware.

GPIO 4-mA Drive Select (GPIODR4R)

GPIO Port A (APB) base: 0x4000.4000 GPIO Port A (AHB) base: 0x4005.8000 GPIO Port B (APB) base: 0x4000.5000 GPIO Port B (AHB) base: 0x4005.9000 GPIO Port C (APB) base: 0x4000.6000 GPIO Port C (AHB) base: 0x4005.A000 GPIO Port D (APB) base: 0x4000.7000 GPIO Port D (AHB) base: 0x4005.B000 GPIO Port E (APB) base: 0x4002.4000 GPIO Port E (AHB) base: 0x4005.C000 GPIO Port F (APB) base: 0x4002.5000 GPIO Port F (AHB) base: 0x4005.D000 GPIO Port G (APB) base: 0x4002.6000 GPIO Port G (AHB) base: 0x4005.E000 GPIO Port H (APB) base: 0x4002.7000 GPIO Port H (AHB) base: 0x4005.F000 GPIO Port J (APB) base: 0x4003.D000 GPIO Port J (AHB) base: 0x4006.0000 GPIO Port K (AHB) base: 0x4006.1000 Offset 0x504

Type R/W, reset 0x0000.0000



Bit/Field	Name	Type	Reset	Description
31:8	reserved	RO	0x0000.00	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
7:0	DRV4	R/W	0x00	Output Pad 4-mA Drive Enable

Value Description

- The drive for the corresponding GPIO pin is controlled by the GPIODR2R or GPIODR8R register.
- 1 The corresponding GPIO pin has 4-mA drive.

Setting a bit in either the GPIODR2 register or the GPIODR8 register clears the corresponding 4-mA enable bit. The change is effective on the second clock cycle after the write if accessing GPIO via the APB memory aperture. If using AHB access, the change is effective on the next clock cycle.


Register 13: GPIO 8-mA Drive Select (GPIODR8R), offset 0x508

The **GPIODR8R** register is the 8-mA drive control register. Each GPIO signal in the port can be individually configured without affecting the other pads. When setting the DRV8 bit for a GPIO signal, the corresponding DRV2 bit in the **GPIODR2R** register and DRV4 bit in the **GPIODR4R** register are automatically cleared by hardware. The 8-mA setting is also used for high-current operation.

Note: There is no configuration difference between 8-mA and high-current operation. The additional current capacity results from a shift in the V_{OH}/V_{OL} levels. See "Recommended Operating Conditions" on page 1378 for further information.

GPIO 8-mA Drive Select (GPIODR8R)

GPIO Port A (APB) base: 0x4000.4000 GPIO Port A (AHB) base: 0x4005.8000 GPIO Port B (APB) base: 0x4000.5000 GPIO Port B (AHB) base: 0x4005.9000 GPIO Port C (APB) base: 0x4000.6000 GPIO Port C (AHB) base: 0x4005.A000 GPIO Port D (APB) base: 0x4000.7000 GPIO Port D (AHB) base: 0x4005.B000 GPIO Port F (APR) base: 0x4002 4000 GPIO Port E (AHB) base: 0x4005.C000 GPIO Port F (APB) base: 0x4002.5000 GPIO Port F (AHB) base: 0x4005.D000 GPIO Port G (APB) base: 0x4002.6000 GPIO Port G (AHB) base: 0x4005.E000 GPIO Port H (APB) base: 0x4002.7000 GPIO Port H (AHB) base: 0x4005.F000 GPIO Port J (APB) base: 0x4003.D000 GPIO Port J (AHB) base: 0x4006.0000 GPIO Port K (AHB) base: 0x4006.1000 Offset 0x508 Type R/W, reset 0x0000.0000



Bit/Field	Name	Type	Reset	Description
31:8	reserved	RO	0x0000.00	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
7:0	DRV8	R/W	0x00	Output Pad 8-mA Drive Enable

Value Description

- The drive for the corresponding GPIO pin is controlled by the GPIODR2R or GPIODR4R register.
- 1 The corresponding GPIO pin has 8-mA drive.

Setting a bit in either the **GPIODR2** register or the **GPIODR4** register clears the corresponding 8-mA enable bit. The change is effective on the second clock cycle after the write if accessing GPIO via the APB memory aperture. If using AHB access, the change is effective on the next clock cycle.


Register 14: GPIO Open Drain Select (GPIOODR), offset 0x50C

The **GPIOODR** register is the open drain control register. Setting a bit in this register enables the open-drain configuration of the corresponding GPIO pad. When open-drain mode is enabled, the corresponding bit should also be set in the **GPIO Digital Enable (GPIODEN)** register (see page 681). Corresponding bits in the drive strength and slew rate control registers (**GPIODR2R**, **GPIODR4R**, **GPIODR8R**, and **GPIOSLR**) can be set to achieve the desired rise and fall times. The GPIO acts as an input if the corresponding bit in the **GPIODIR** register is cleared. If open drain is selected while the GPIO is configured as an input, the GPIO will remain an input and the open-drain selection has no effect until the GPIO is changed to an output.

When using the I²C module, in addition to configuring the pin to open drain, the **GPIO Alternate Function Select (GPIOAFSEL)** register bits for the I²C data pins should be set (see examples in "Initialization and Configuration" on page 654).

GPIO Open Drain Select (GPIOODR)

GPIO Port A (APB) base: 0x4000.4000 GPIO Port A (AHB) base: 0x4005.8000 GPIO Port B (APB) base: 0x4000.5000 GPIO Port B (AHB) base: 0x4005.9000 GPIO Port C (APB) base: 0x4000.6000 GPIO Port C (AHB) base: 0x4005.A000 GPIO Port D (APB) base: 0x4000.7000 GPIO Port D (AHB) base: 0x4005.B000 GPIO Port E (APB) base: 0x4002.4000 GPIO Port E (AHB) base: 0x4005.C000 GPIO Port F (APB) base: 0x4002.5000 GPIO Port F (AHB) base: 0x4005.D000 GPIO Port G (APB) base: 0x4002.6000 GPIO Port G (AHB) base: 0x4005.E000 GPIO Port H (APB) base: 0x4002.7000 GPIO Port H (AHB) base: 0x4005.F000 GPIO Port J (APB) base: 0x4003.D000 GPIO Port J (AHB) base: 0x4006.0000 GPIO Port K (AHB) base: 0x4006.1000 Offset 0x50C



Bit/Field	Name	Type	Reset	Description
31:8	reserved	RO	0x0000.00	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
7:0	ODE	R/W	0x00	Output Pad Open Drain Enable

- 0 The corresponding pin is not configured as open drain.
- 1 The corresponding pin is configured as open drain.

Register 15: GPIO Pull-Up Select (GPIOPUR), offset 0x510

The **GPIOPUR** register is the pull-up control register. When a bit is set, a weak pull-up resistor on the corresponding GPIO signal is enabled. Setting a bit in **GPIOPUR** automatically clears the corresponding bit in the **GPIO Pull-Down Select (GPIOPDR)** register (see page 678). Write access to this register is protected with the **GPIOCR** register. Bits in **GPIOCR** that are cleared prevent writes to the equivalent bit in this register.

Important: All GPIO pins are configured as GPIOs and tri-stated by default (GPIOAFSEL=0, GPIODEN=0, GPIOPDR=0, GPIOPUR=0, and GPIOPCTL=0), with the exception of the pins shown in the table below. A Power-On-Reset (POR) or asserting RST puts the pins back to their default state.

Table 10-8. GPIO Pins With Non-Zero Reset Values


GPIO Pins	Default State	GPIOAFSEL	GPIODEN	GPIOPDR	GPIOPUR	GPIOPCTL
PA[1:0]	UART0	0	0	0	0	0x1
PA[5:2]	SSI0	0	0	0	0	0x2
PB[3:2]	I ² C0	0	0	0	0	0x3
PC[3:0]	JTAG/SWD	1	1	0	1	0x1

The GPIO commit control registers provide a layer of protection against accidental programming of critical hardware signals including the GPIO pins that can function as JTAG/SWD signals and the NMI signal. The commit control process must be followed for these pins, even if they are programmed as alternate functions other than JTAG/SWD or NMI, see "Commit Control" on page 654.

Note: The GPIO commit control registers provide a layer of protection against accidental programming of critical hardware peripherals. Protection is provided for the GPIO pins that can be used as the four JTAG/SWD pins (PC[3:0]) and the NMI pin (PD7 and PF0). Writes to protected bits of the GPIO Alternate Function Select (GPIOAFSEL) register (see page 670), GPIO Pull Up Select (GPIOPUR) register (see page 676), GPIO Pull-Down Select (GPIOPDR) register (see page 678), and GPIO Digital Enable (GPIODEN) register (see page 681) are not committed to storage unless the GPIO Lock (GPIOLOCK) register (see page 683) has been unlocked and the appropriate bits of the GPIO Commit (GPIOCR) register (see page 684) have been set.

GPIO Pull-Up Select (GPIOPUR)

GPIO Port A (APB) base: 0x4000.4000 GPIO Port A (AHB) base: 0x4005.8000 GPIO Port B (APB) base: 0x4005.8000 GPIO Port B (APB) base: 0x4005.9000 GPIO Port C (APB) base: 0x4005.9000 GPIO Port C (AHB) base: 0x4005.4000 GPIO Port D (APB) base: 0x4005.4000 GPIO Port D (APB) base: 0x4005.8000 GPIO Port D (APB) base: 0x4005.8000 GPIO Port E (APB) base: 0x4002.4000 GPIO Port E (AHB) base: 0x4002.5000 GPIO Port F (APB) base: 0x4005.0000 GPIO Port F (APB) base: 0x4005.0000 GPIO Port G (APB) base: 0x4005.0000 GPIO Port G (APB) base: 0x4005.0000 GPIO Port G (AHB) base: 0x4002.7000 GPIO Port H (APB) base: 0x4005.7000 GPIO Port H (APB) base: 0x4005.7000 GPIO Port J (AHB) base: 0x4006.0000 GPIO Port K (AHB) base: 0x4006.1000 OFISet 0x510



Bit/Field	Name	Type	Reset	Description
31:8	reserved	RO	0x0000.00	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
7:0	PUE	R/W	-	Pad Weak Pull-Up Enable

Value Description

- 0 The corresponding pin's weak pull-up resistor is disabled.
- 1 The corresponding pin's weak pull-up resistor is enabled.

Setting a bit in the **GPIOPDR** register clears the corresponding bit in the **GPIOPUR** register. The change is effective on the second clock cycle after the write if accessing GPIO via the APB memory aperture. If using AHB access, the change is effective on the next clock cycle.

The reset value for this register is 0x0000.0000 for GPIO ports that are not listed in Table 10-1 on page 647.

Register 16: GPIO Pull-Down Select (GPIOPDR), offset 0x514

The **GPIOPDR** register is the pull-down control register. When a bit is set, a weak pull-down resistor on the corresponding GPIO signal is enabled. Setting a bit in **GPIOPDR** automatically clears the corresponding bit in the **GPIO Pull-Up Select (GPIOPUR)** register (see page 676).

Important: All GPIO pins are configured as GPIOs and tri-stated by default (GPIOAFSEL=0, GPIODEN=0, GPIOPDR=0, GPIOPUR=0, and GPIOPCTL=0), with the exception of the pins shown in the table below. A Power-On-Reset (POR) or asserting RST puts the pins back to their default state.

Table 10-9, GPIO Pins With Non-Zero Reset Values


GPIO Pins	Default State	GPIOAFSEL	GPIODEN	GPIOPDR	GPIOPUR	GPIOPCTL
PA[1:0]	UART0	0	0	0	0	0x1
PA[5:2]	SSI0	0	0	0	0	0x2
PB[3:2]	I ² C0	0	0	0	0	0x3
PC[3:0]	JTAG/SWD	1	1	0	1	0x1

The GPIO commit control registers provide a layer of protection against accidental programming of critical hardware signals including the GPIO pins that can function as JTAG/SWD signals and the NMI signal. The commit control process must be followed for these pins, even if they are programmed as alternate functions other than JTAG/SWD or NMI, see "Commit Control" on page 654.

Note: The GPIO commit control registers provide a layer of protection against accidental programming of critical hardware peripherals. Protection is provided for the GPIO pins that can be used as the four JTAG/SWD pins (PC[3:0]) and the NMI pin (PD7 and PF0). Writes to protected bits of the GPIO Alternate Function Select (GPIOAFSEL) register (see page 670), GPIO Pull Up Select (GPIOPUR) register (see page 676), GPIO Pull-Down Select (GPIOPDR) register (see page 678), and GPIO Digital Enable (GPIODEN) register (see page 681) are not committed to storage unless the GPIO Lock (GPIOLOCK) register (see page 683) has been unlocked and the appropriate bits of the GPIO Commit (GPIOCR) register (see page 684) have been set.

GPIO Pull-Down Select (GPIOPDR)

GPIO Port A (APB) base: 0x4000.4000 GPIO Port A (AHB) base: 0x4005.8000 GPIO Port B (APB) base: 0x4005.8000 GPIO Port B (APB) base: 0x4005.9000 GPIO Port C (APB) base: 0x4005.9000 GPIO Port C (APB) base: 0x4005.4000 GPIO Port C (AHB) base: 0x4000.7000 GPIO Port D (APB) base: 0x4005.8000 GPIO Port D (APB) base: 0x4005.8000 GPIO Port E (APB) base: 0x4002.4000 GPIO Port E (APB) base: 0x4002.5000 GPIO Port F (APB) base: 0x4002.5000 GPIO Port F (APB) base: 0x4002.5000 GPIO Port G (APB) base: 0x4002.5000 GPIO Port G (APB) base: 0x4002.5000 GPIO Port G (APB) base: 0x4002.7000 GPIO Port H (APB) base: 0x4002.7000 GPIO Port H (APB) base: 0x4005.F000 GPIO Port J (APB) base: 0x4006.0000 GPIO Port K (AHB) base: 0x4006.1000 Offset 0x514



Bit/Field	Name	Туре	Reset	Description
31:8	reserved	RO	0x0000.00	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
7:0	PDE	R/W	0x00	Pad Weak Pull-Down Enable

Value Description

- 0 The corresponding pin's weak pull-down resistor is disabled.
- 1 The corresponding pin's weak pull-down resistor is enabled.


Setting a bit in the **GPIOPUR** register clears the corresponding bit in the **GPIOPDR** register. The change is effective on the second clock cycle after the write if accessing GPIO via the APB memory aperture. If using AHB access, the change is effective on the next clock cycle.

Register 17: GPIO Slew Rate Control Select (GPIOSLR), offset 0x518

The **GPIOSLR** register is the slew rate control register. Slew rate control is only available when using the 8-mA drive strength option via the **GPIO 8-mA Drive Select (GPIODR8R)** register (see page 674).

GPIO Slew Rate Control Select (GPIOSLR)

GPIO Port A (APB) base: 0x4000.4000 GPIO Port A (AHB) base: 0x4005.8000 GPIO Port B (APB) base: 0x4000.5000 GPIO Port B (AHB) base: 0x4005.9000 GPIO Port C (APB) base: 0x4000.6000 GPIO Port C (AHB) base: 0x4005.A000 GPIO Port D (APB) base: 0x4000.7000 GPIO Port D (AHB) base: 0x4005.B000 GPIO Port E (APB) base: 0x4002.4000 GPIO Port E (AHB) base: 0x4005.C000 GPIO Port F (APB) base: 0x4002.5000 GPIO Port F (AHB) base: 0x4005.D000 GPIO Port G (APB) base: 0x4002.6000 GPIO Port G (AHB) base: 0x4005.E000 GPIO Port H (APB) base: 0x4002.7000 GPIO Port H (AHB) base: 0x4005.F000 GPIO Port J (APB) base: 0x4003.D000 GPIO Port J (AHB) base: 0x4006.0000 GPIO Port K (AHB) base: 0x4006.1000 Offset 0x518 Type R/W, reset 0x0000.0000



Bit/Field	Name	Туре	Reset	Description
31:8	reserved	RO	0x0000.00	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
7:0	SRL	R/W	0x00	Slew Rate Limit Enable (8-mA drive only)

- 0 Slew rate control is disabled for the corresponding pin.
- 1 Slew rate control is enabled for the corresponding pin.

Register 18: GPIO Digital Enable (GPIODEN), offset 0x51C

Note: Pins configured as digital inputs are Schmitt-triggered.

The **GPIODEN** register is the digital enable register. By default, all GPIO signals except those listed below are configured out of reset to be undriven (tristate). Their digital function is disabled; they do not drive a logic value on the pin and they do not allow the pin voltage into the GPIO receiver. To use the pin as a digital input or output (either GPIO or alternate function), the corresponding GPIODEN bit must be set.

Important: All GPIO pins are configured as GPIOs and tri-stated by default (GPIOAFSEL=0, GPIODEN=0, GPIOPDR=0, GPIOPUR=0, and GPIOPCTL=0), with the exception of the pins shown in the table below. A Power-On-Reset (POR) or asserting RST puts the pins back to their default state.

Table 10-10, GPIO Pins With Non-Zero Reset Values


GPIO Pins	Default State	GPIOAFSEL	GPIODEN	GPIOPDR	GPIOPUR	GPIOPCTL
PA[1:0]	UART0	0	0	0	0	0x1
PA[5:2]	SSI0	0	0	0	0	0x2
PB[3:2]	I ² C0	0	0	0	0	0x3
PC[3:0]	JTAG/SWD	1	1	0	1	0x1

The GPIO commit control registers provide a layer of protection against accidental programming of critical hardware signals including the GPIO pins that can function as JTAG/SWD signals and the NMI signal. The commit control process must be followed for these pins, even if they are programmed as alternate functions other than JTAG/SWD or NMI, see "Commit Control" on page 654.

Note: The GPIO commit control registers provide a layer of protection against accidental programming of critical hardware peripherals. Protection is provided for the GPIO pins that can be used as the four JTAG/SWD pins (PC[3:0]) and the NMI pin (PD7 and PF0). Writes to protected bits of the GPIO Alternate Function Select (GPIOAFSEL) register (see page 670), GPIO Pull Up Select (GPIOPUR) register (see page 676), GPIO Pull-Down Select (GPIOPDR) register (see page 678), and GPIO Digital Enable (GPIODEN) register (see page 681) are not committed to storage unless the GPIO Lock (GPIOLOCK) register (see page 683) has been unlocked and the appropriate bits of the GPIO Commit (GPIOCR) register (see page 684) have been set.

GPIO Digital Enable (GPIODEN)

GPIO Port A (APB) base: 0x4000.4000 GPIO Port A (AHB) base: 0x4005.8000 GPIO Port B (APB) base: 0x4005.8000 GPIO Port B (AHB) base: 0x4005.9000 GPIO Port C (APB) base: 0x4000.6000 GPIO Port C (AHB) base: 0x4000.6000 GPIO Port C (AHB) base: 0x4005.A000 GPIO Port D (AHB) base: 0x4005.A000 GPIO Port D (AHB) base: 0x4005.B000 GPIO Port E (APB) base: 0x4002.4000 GPIO Port E (AHB) base: 0x4002.5000 GPIO Port F (APB) base: 0x4005.5000 GPIO Port F (APB) base: 0x4005.5000 GPIO Port G (APB) base: 0x4005.5000 GPIO Port G (AHB) base: 0x4005.E000 GPIO Port H (APB) base: 0x4002.7000 GPIO Port H (APB) base: 0x4005.F000 GPIO Port H (APB) base: 0x4005.F000 GPIO Port J (AHB) base: 0x4006.0000 GPIO Port K (AHB) base: 0x4006.1000 OFISet 0x51C



Bit/Field	Name	Type	Reset	Description
31:8	reserved	RO	0x0000.00	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
7:0	DEN	R/W	-	Digital Enable

- 0 The digital functions for the corresponding pin are disabled.
- The digital functions for the corresponding pin are enabled.

 The reset value for this register is 0x0000.0000 for GPIO ports that are not listed in Table 10-1 on page 647.


Register 19: GPIO Lock (GPIOLOCK), offset 0x520

The **GPIOLOCK** register enables write access to the **GPIOCR** register (see page 684). Writing 0x4C4F.434B to the **GPIOLOCK** register unlocks the **GPIOCR** register. Writing any other value to the **GPIOLOCK** register re-enables the locked state. Reading the **GPIOLOCK** register returns the lock status rather than the 32-bit value that was previously written. Therefore, when write accesses are disabled, or locked, reading the **GPIOLOCK** register returns 0x0000.0001. When write accesses are enabled, or unlocked, reading the **GPIOLOCK** register returns 0x0000.0000.

GPIO Lock (GPIOLOCK)

GPIO Port A (APB) base: 0x4000.4000 GPIO Port A (AHB) base: 0x4005.8000 GPIO Port B (APB) base: 0x4000.5000 GPIO Port B (AHB) base: 0x4005.9000 GPIO Port C (APB) base: 0x4000.6000 GPIO Port C (AHB) base: 0x4005.A000 GPIO Port D (APB) base: 0x4000.7000 GPIO Port D (AHB) base: 0x4005.B000 GPIO Port E (APB) base: 0x4002.4000 GPIO Port E (AHB) base: 0x4005.C000 GPIO Port F (APB) base: 0x4002.5000 GPIO Port F (AHB) base: 0x4005.D000 GPIO Port G (APB) base: 0x4002.6000 GPIO Port G (AHB) base: 0x4005.E000 GPIO Port H (APB) base: 0x4002.7000 GPIO Port H (AHB) base: 0x4005.F000 GPIO Port J (APB) base: 0x4003.D000 GPIO Port J (AHB) base: 0x4006.0000 GPIO Port K (AHB) base: 0x4006.1000 Offset 0x520

Type R/W, reset 0x0000.0001



Bit/Field	Name	Туре	Reset	Description
31:0	LOCK	R/W	0x0000.0001	GPIO Lock

A write of the value 0x4C4F.434B unlocks the **GPIO Commit (GPIOCR)** register for write access.A write of any other value or a write to the **GPIOCR** register reapplies the lock, preventing any register updates.

A read of this register returns the following values:

Value Description

0x1 The **GPIOCR** register is locked and may not be modified.

0x0 The **GPIOCR** register is unlocked and may be modified.

Register 20: GPIO Commit (GPIOCR), offset 0x524

The GPIOCR register is the commit register. The value of the GPIOCR register determines which bits of the GPIOAFSEL, GPIOPUR, GPIOPDR, and GPIODEN registers are committed when a write to these registers is performed. If a bit in the **GPIOCR** register is cleared, the data being written to the corresponding bit in the GPIOAFSEL, GPIOPUR, GPIOPDR, or GPIODEN registers cannot be committed and retains its previous value. If a bit in the **GPIOCR** register is set, the data being written to the corresponding bit of the GPIOAFSEL, GPIOPUR, GPIOPDR, or GPIODEN registers is committed to the register and reflects the new value.


The contents of the GPIOCR register can only be modified if the status in the GPIOLOCK register is unlocked. Writes to the GPIOCR register are ignored if the status in the GPIOLOCK register is locked.

Important: This register is designed to prevent accidental programming of the registers that control connectivity to the NMI and JTAG/SWD debug hardware. By initializing the bits of the **GPIOCR** register to 0 for PD7, PF0, and PC[3:0], the NMI and JTAG/SWD debug port can only be converted to GPIOs through a deliberate set of writes to the GPIOLOCK, **GPIOCR**, and the corresponding registers.

> Because this protection is currently only implemented on the NMI and JTAG/SWD pins on PD7, PF0, and PC[3:0], all of the other bits in the GPIOCR registers cannot be written with 0x0. These bits are hardwired to 0x1, ensuring that it is always possible to commit new values to the GPIOAFSEL, GPIOPUR, GPIOPDR, or GPIODEN register bits of these other pins.

GPIO Commit (GPIOCR)

GPIO Port A (APB) base: 0x4000.4000 GPIO Port A (AHB) base: 0x4005.8000 GPIO Port B (APB) base: 0x4000.5000 GPIO Port B (AHB) base: 0x4005.9000 GPIO Port C (APB) base: 0x4000.6000 GPIO Port C (AHB) base: 0x4005.A000 GPIO Port D (APB) base: 0x4000.7000 GPIO Port D (AHB) base: 0x4005.B000 GPIO Port E (APB) base: 0x4002.4000 GPIO Port E (AHB) base: 0x4005.C000 GPIO Port F (APB) base: 0x4002.5000 GPIO Port F (AHB) base: 0x4005.D000 GPIO Port G (APB) base: 0x4002.6000 GPIO Port G (AHB) base: 0x4005.E000 GPIO Port H (APB) base: 0x4002.7000 GPIO Port H (AHB) base: 0x4005.F000 GPIO Port J (APB) base: 0x4003.D000 GPIO Port J (AHB) base: 0x4006.0000 GPIO Port K (AHB) base: 0x4006.1000 Offset 0x524 Type -, reset -



Bit/Field	Name	Type	Reset	Description
31:8	reserved	RO	0x0000.00	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
7:0	CR	-	-	GPIO Commit

Value Description

- The corresponding GPIOAFSEL, GPIOPUR, GPIOPDR, or GPIODEN bits cannot be written.
- 1 The corresponding GPIOAFSEL, GPIOPUR, GPIOPDR, or GPIODEN bits can be written.

Note:

The default register type for the **GPIOCR** register is RO for all GPIO pins with the exception of the NMI pin and the four JTAG/SWD pins (PD7, PF0, and PC[3:0]). These six pins are the only GPIOs that are protected by the **GPIOCR** register. Because of this, the register type for GPIO Port D7, GPIO Port F0, and GPIO Port C[3:0] is R/W.

The default reset value for the **GPIOCR** register is 0x0000.00FF for all GPIO pins, with the exception of the NMI pin and the four JTAG/SWD pins (PD7, PF0, and PC[3:0]). To ensure that the JTAG port is not accidentally programmed as GPIO pins, the PC[3:0] pins default to non-committable. Similarly, to ensure that the NMI pin is not accidentally programmed as a GPIO pin, the PD7 and PF0 pins default to non-committable. Because of this, the default reset value of **GPIOCR** for GPIO Port C is 0x0000.00F0, for GPIO Port D is 0x0000.00FF, and for GPIO Port F is 0x0000.00FE.

Register 21: GPIO Analog Mode Select (GPIOAMSEL), offset 0x528

Important: This register is only valid for ports and pins that can be used as ADC AINx inputs.


If any pin is to be used as an ADC input, the appropriate bit in **GPIOAMSEL** must be set to disable the analog isolation circuit.

The **GPIOAMSEL** register controls isolation circuits to the analog side of a unified I/O pad. Because the GPIOs may be driven by a 5-V source and affect analog operation, analog circuitry requires isolation from the pins when they are not used in their analog function.

Each bit of this register controls the isolation circuitry for the corresponding GPIO signal. For information on which GPIO pins can be used for ADC functions, refer to Table 23-5 on page 1367.

GPIO Analog Mode Select (GPIOAMSEL)

GPIO Port A (APB) base: 0x4000.4000 GPIO Port A (AHB) base: 0x4005.8000 GPIO Port B (APB) base: 0x4000.5000 GPIO Port B (AHB) base: 0x4005.9000 GPIO Port C (APB) base: 0x4000.6000 GPIO Port C (AHB) base: 0x4005.A000 GPIO Port D (APB) base: 0x4000.7000 GPIO Port D (AHB) base: 0x4005.B000 GPIO Port E (APB) base: 0x4002.4000 GPIO Port E (AHB) base: 0x4005.C000 GPIO Port F (APB) base: 0x4002.5000 GPIO Port F (AHB) base: 0x4005.D000 GPIO Port G (APB) base: 0x4002.6000 GPIO Port G (AHB) base: 0x4005.E000 GPIO Port H (APB) base: 0x4002.7000 GPIO Port H (AHB) base: 0x4005.F000 GPIO Port J (APB) base: 0x4003.D000 GPIO Port J (AHB) base: 0x4006.0000 GPIO Port K (AHB) base: 0x4006.1000 Offset 0x528



Bit/Field Name Type Reset Description

31:8 reserved RO 0x0000.00 Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.

Bit/Field	Name	Type	Reset	Description
7:0	GPIOAMSEL	R/W	0x00	GPIO Analog Mode Select

Value Description

- The analog function of the pin is disabled, the isolation is enabled, and the pin is capable of digital functions as specified by the other GPIO configuration registers.
- 1 The analog function of the pin is enabled, the isolation is disabled, and the pin is capable of analog functions.

Note: This register and bits are only valid for GPIO signals that share analog function through a unified I/O pad.

The reset state of this register is 0 for all signals.

Register 22: GPIO Port Control (GPIOPCTL), offset 0x52C

The **GPIOPCTL** register is used in conjunction with the **GPIOAFSEL** register and selects the specific peripheral signal for each GPIO pin when using the alternate function mode. Most bits in the **GPIOAFSEL** register are cleared on reset, therefore most GPIO pins are configured as GPIOs by default. When a bit is set in the **GPIOAFSEL** register, the corresponding GPIO signal is controlled by an associated peripheral. The **GPIOPCTL** register selects one out of a set of peripheral functions for each GPIO, providing additional flexibility in signal definition. For information on the defined encodings for the bit fields in this register, refer to Table 23-5 on page 1367. The reset value for this register is 0x0000.0000 for GPIO ports that are not listed in the table below.

Note: If the same signal is assigned to two different GPIO port pins configured as inputs, the signal is assigned to the port with the lowest letter and the assignment to the higher letter port is ignored. If the same signal is assigned to two different GPIO port pins configured as outputs, the signal will output to both pins.

Important: All GPIO pins are configured as GPIOs and tri-stated by default (GPIOAFSEL=0, GPIODEN=0, GPIOPDR=0, GPIOPUR=0, and GPIOPCTL=0), with the exception of the pins shown in the table below. A Power-On-Reset (POR) or asserting RST puts the pins back to their default state.

Table 10-11, GPIO Pins With Non-Zero Reset Values

GPIO Pins	Default State	GPIOAFSEL	GPIODEN	GPIOPDR	GPIOPUR	GPIOPCTL
PA[1:0]	UART0	0	0	0	0	0x1
PA[5:2]	SSI0	0	0	0	0	0x2
PB[3:2]	I ² C0	0	0	0	0	0x3
PC[3:0]	JTAG/SWD	1	1	0	1	0x1

The GPIO commit control registers provide a layer of protection against accidental programming of critical hardware signals including the GPIO pins that can function as JTAG/SWD signals and the NMI signal. The commit control process must be followed for these pins, even if they are programmed as alternate functions other than JTAG/SWD or NMI, see "Commit Control" on page 654.

GPIO Port Control (GPIOPCTL)

GPIO Port A (APB) base: 0x4000.4000
GPIO Port A (AHB) base: 0x4005.8000
GPIO Port B (APB) base: 0x4005.9000
GPIO Port B (AHB) base: 0x4005.9000
GPIO Port C (APB) base: 0x4005.9000
GPIO Port C (APB) base: 0x4005.A000
GPIO Port C (AHB) base: 0x4005.A000
GPIO Port D (AHB) base: 0x4005.B000
GPIO Port D (AHB) base: 0x4005.B000
GPIO Port E (APB) base: 0x4005.C000
GPIO Port E (AHB) base: 0x4002.4000
GPIO Port F (AHB) base: 0x4005.C000
GPIO Port F (AHB) base: 0x4005.D000
GPIO Port G (AHB) base: 0x4005.D000
GPIO Port G (AHB) base: 0x4002.6000
GPIO Port G (AHB) base: 0x4002.7000
GPIO Port H (AHB) base: 0x4005.E000
GPIO Port J (APB) base: 0x4005.E000
GPIO Port J (APB) base: 0x4005.D000
GPIO Port J (AHB) base: 0x4003.D000
GPIO Port J (AHB) base: 0x4006.1000
GPIO Port K (AHB) base: 0x4006.1000
Offset 0x52C
Type R/W, reset -

	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16
		PM	IC7	1		PM	IC6	1		PM	C5			PM	C4	
Type Reset	R/W -															
	15	14	13	12	11	10	9	8	7	6	5	4	3	2	1	0
		PM	IC3	•		PM	IC2	•		PM	C1			PM	C0	
Туре	R/W															
Reset	-	_	-	-	-	_	_	-	_	-	-	-	_	-	-	_

Bit/Field	Name	Туре	Reset	Description
31:28	PMC7	R/W	-	Port Mux Control 7 This field controls the configuration for GPIO pin 7.
27:24	PMC6	R/W	-	Port Mux Control 6 This field controls the configuration for GPIO pin 6.
23:20	PMC5	R/W	-	Port Mux Control 5 This field controls the configuration for GPIO pin 5.
19:16	PMC4	R/W	-	Port Mux Control 4 This field controls the configuration for GPIO pin 4.
15:12	PMC3	R/W	-	Port Mux Control 3 This field controls the configuration for GPIO pin 3.
11:8	PMC2	R/W	-	Port Mux Control 2 This field controls the configuration for GPIO pin 2.
7:4	PMC1	R/W	-	Port Mux Control 1 This field controls the configuration for GPIO pin 1.
3:0	PMC0	R/W	-	Port Mux Control 0 This field controls the configuration for GPIO pin 0.


Register 23: GPIO ADC Control (GPIOADCCTL), offset 0x530

This register is used to configure a GPIO pin as a source for the ADC trigger.

Note that if the Port B **GPIOADCCTL** register is cleared, PB4 can still be used as an external trigger for the ADC. This is a legacy mode which allows code written for previous Stellaris devices to operate on this microcontroller.

GPIO ADC Control (GPIOADCCTL)

GPIO Port A (APB) base: 0x4000.4000 GPIO Port A (AHB) base: 0x4005.8000 GPIO Port B (APB) base: 0x4000.5000 GPIO Port B (AHB) base: 0x4005.9000 GPIO Port C (APB) base: 0x4000.6000 GPIO Port C (AHB) base: 0x4005.A000 GPIO Port D (APB) base: 0x4000.7000 GPIO Port D (AHB) base: 0x4005.B000 GPIO Port E (APB) base: 0x4002.4000 GPIO Port E (AHB) base: 0x4005.C000 GPIO Port F (APB) base: 0x4002.5000 GPIO Port F (AHB) base: 0x4005.D000 GPIO Port G (APB) base: 0x4002.6000 GPIO Port G (AHB) base: 0x4005.E000 GPIO Port H (APB) base: 0x4002.7000 GPIO Port H (AHB) base: 0x4005.F000 GPIO Port J (APB) base: 0x4003.D000 GPIO Port J (AHB) base: 0x4006.0000 GPIO Port K (AHB) base: 0x4006.1000 Offset 0x530 Type R/W, reset 0x0000.0000



Bit/Field	Name	Type	Reset	Description
31:8	reserved	RO	0x0000.00	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
7:0	ADCEN	R/W	0x00	ADC Trigger Enable

Value Description

- 0 The corresponding pin is not used to trigger the ADC.
- 1 The corresponding pin is used to trigger the ADC.


Register 24: GPIO DMA Control (GPIODMACTL), offset 0x534

This register is used to configure a GPIO pin as a source for the µDMA trigger.

GPIO DMA Control (GPIODMACTL)

GPIO Port A (APB) base: 0x4000.4000 GPIO Port A (AHB) base: 0x4005.8000 GPIO Port B (APB) base: 0x4000.5000 GPIO Port B (AHB) base: 0x4005.9000 GPIO Port C (APB) base: 0x4000.6000 GPIO Port C (AHB) base: 0x4005.A000 GPIO Port D (APB) base: 0x4000.7000 GPIO Port D (AHB) base: 0x4005.B000 GPIO Port E (APB) base: 0x4002.4000 GPIO Port E (AHB) base: 0x4005.C000 GPIO Port F (APB) base: 0x4002.5000 GPIO Port F (AHB) base: 0x4005.D000 GPIO Port G (APB) base: 0x4002.6000 GPIO Port G (AHB) base: 0x4005.E000 GPIO Port H (APB) base: 0x4002.7000 GPIO Port H (AHB) base: 0x4005.F000 GPIO Port J (APB) base: 0x4003.D000 GPIO Port J (AHB) base: 0x4006.0000 GPIO Port K (AHB) base: 0x4006.1000 Offset 0x534

Type R/W, reset 0x0000.0000



Bit/Field	Name	Type	Reset	Description
31:8	reserved	RO	0x0000.00	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
7:0	DMAEN	R/W	0x00	μDMA Trigger Enable

Value Description


- 0 The corresponding pin is not used to trigger the μDMA .
- 1 The corresponding pin is used to trigger the μ DMA.

Register 25: GPIO Peripheral Identification 4 (GPIOPeriphID4), offset 0xFD0

The GPIOPeriphID4, GPIOPeriphID5, GPIOPeriphID6, and GPIOPeriphID7 registers can conceptually be treated as one 32-bit register; each register contains eight bits of the 32-bit register, used by software to identify the peripheral.

GPIO Peripheral Identification 4 (GPIOPeriphID4)

GPIO Port A (APB) base: 0x4000.4000 GPIO Port A (AHB) base: 0x4005.8000 GPIO Port B (APB) base: 0x4000.5000 GPIO Port B (AHB) base: 0x4005.9000 GPIO Port C (APB) base: 0x4000.6000 GPIO Port C (AHB) base: 0x4005.A000 GPIO Port D (APB) base: 0x4000.7000 GPIO Port D (AHB) base: 0x4005.B000 GPIO Port E (APB) base: 0x4002.4000 GPIO Port E (AHB) base: 0x4005.C000 GPIO Port F (APB) base: 0x4002.5000 GPIO Port F (AHB) base: 0x4005.D000 GPIO Port G (APB) base: 0x4002.6000 GPIO Port G (AHB) base: 0x4005.E000 GPIO Port H (APB) base: 0x4002.7000 GPIO Port H (AHB) base: 0x4005.F000 GPIO Port J (APB) base: 0x4003.D000 GPIO Port J (AHB) base: 0x4006.0000 GPIO Port K (AHB) base: 0x4006.1000 Offset 0xFD0 Type RO, reset 0x0000.0000




Bit/Field	Name	Type	Reset	Description
31:8	reserved	RO	0x0000.00	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
7:0	PID4	RO	0x00	GPIO Peripheral ID Register [7:0]

Register 26: GPIO Peripheral Identification 5 (GPIOPeriphID5), offset 0xFD4

The **GPIOPeriphID4**, **GPIOPeriphID5**, **GPIOPeriphID6**, and **GPIOPeriphID7** registers can conceptually be treated as one 32-bit register; each register contains eight bits of the 32-bit register, used by software to identify the peripheral.

GPIO Peripheral Identification 5 (GPIOPeriphID5)

GPIO Port A (APB) base: 0x4000.4000 GPIO Port A (AHB) base: 0x4005.8000 GPIO Port B (APB) base: 0x4000.5000 GPIO Port B (AHB) base: 0x4005.9000 GPIO Port C (APB) base: 0x4000.6000 GPIO Port C (AHB) base: 0x4005.A000 GPIO Port D (APB) base: 0x4000.7000 GPIO Port D (AHB) base: 0x4005.B000 GPIO Port E (APB) base: 0x4002.4000 GPIO Port E (AHB) base: 0x4005.C000 GPIO Port F (APB) base: 0x4002.5000 GPIO Port F (AHB) base: 0x4005.D000 GPIO Port G (APB) base: 0x4002.6000 GPIO Port G (AHB) base: 0x4005.E000 GPIO Port H (APB) base: 0x4002.7000 GPIO Port H (AHB) base: 0x4005.F000 GPIO Port J (APB) base: 0x4003.D000 GPIO Port J (AHB) base: 0x4006.0000 GPIO Port K (AHB) base: 0x4006.1000 Offset 0xFD4 Type RO, reset 0x0000.0000




Bit/Field	Name	Type	Reset	Description
31:8	reserved	RO	0x0000.00	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
7:0	PID5	RO	0x00	GPIO Peripheral ID Register [15:8]

Register 27: GPIO Peripheral Identification 6 (GPIOPeriphID6), offset 0xFD8

The **GPIOPeriphID4**, **GPIOPeriphID5**, **GPIOPeriphID6**, and **GPIOPeriphID7** registers can conceptually be treated as one 32-bit register; each register contains eight bits of the 32-bit register, used by software to identify the peripheral.

GPIO Peripheral Identification 6 (GPIOPeriphID6)

GPIO Port A (APB) base: 0x4000.4000 GPIO Port A (AHB) base: 0x4005.8000 GPIO Port B (APB) base: 0x4000.5000 GPIO Port B (AHB) base: 0x4005.9000 GPIO Port C (APB) base: 0x4000.6000 GPIO Port C (AHB) base: 0x4005.A000 GPIO Port D (APB) base: 0x4000.7000 GPIO Port D (AHB) base: 0x4005.B000 GPIO Port E (APB) base: 0x4002.4000 GPIO Port E (AHB) base: 0x4005.C000 GPIO Port F (APB) base: 0x4002.5000 GPIO Port F (AHB) base: 0x4005.D000 GPIO Port G (APB) base: 0x4002.6000 GPIO Port G (AHB) base: 0x4005.E000 GPIO Port H (APB) base: 0x4002.7000 GPIO Port H (AHB) base: 0x4005.F000 GPIO Port J (APB) base: 0x4003.D000 GPIO Port J (AHB) base: 0x4006.0000 GPIO Port K (AHB) base: 0x4006.1000 Offset 0xFD8 Type RO, reset 0x0000.0000




Bit/Field	Name	Type	Reset	Description
31:8	reserved	RO	0x0000.00	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
7:0	PID6	RO	0x00	GPIO Peripheral ID Register [23:16]

Register 28: GPIO Peripheral Identification 7 (GPIOPeriphID7), offset 0xFDC

The **GPIOPeriphID4**, **GPIOPeriphID5**, **GPIOPeriphID6**, and **GPIOPeriphID7** registers can conceptually be treated as one 32-bit register; each register contains eight bits of the 32-bit register, used by software to identify the peripheral.

GPIO Peripheral Identification 7 (GPIOPeriphID7)

GPIO Port A (APB) base: 0x4000.4000 GPIO Port A (AHB) base: 0x4005.8000 GPIO Port B (APB) base: 0x4000.5000 GPIO Port B (AHB) base: 0x4005.9000 GPIO Port C (APB) base: 0x4000.6000 GPIO Port C (AHB) base: 0x4005.A000 GPIO Port D (APB) base: 0x4000.7000 GPIO Port D (AHB) base: 0x4005.B000 GPIO Port E (APB) base: 0x4002.4000 GPIO Port E (AHB) base: 0x4005.C000 GPIO Port F (APB) base: 0x4002.5000 GPIO Port F (AHB) base: 0x4005.D000 GPIO Port G (APB) base: 0x4002.6000 GPIO Port G (AHB) base: 0x4005.E000 GPIO Port H (APB) base: 0x4002.7000 GPIO Port H (AHB) base: 0x4005.F000 GPIO Port J (APB) base: 0x4003.D000 GPIO Port J (AHB) base: 0x4006.0000 GPIO Port K (AHB) base: 0x4006.1000 Offset 0xFDC Type RO, reset 0x0000.0000



Bit/Field	Name	Type	Reset	Description
31:8	reserved	RO	0x0000.00	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
7:0	PID7	RO	0x00	GPIO Peripheral ID Register [31:24]

Register 29: GPIO Peripheral Identification 0 (GPIOPeriphID0), offset 0xFE0


The **GPIOPeriphID0**, **GPIOPeriphID1**, **GPIOPeriphID2**, and **GPIOPeriphID3** registers can conceptually be treated as one 32-bit register; each register contains eight bits of the 32-bit register, used by software to identify the peripheral.

GPIO Peripheral Identification 0 (GPIOPeriphID0)

Name

GPIO Port A (APB) base: 0x4000.4000 GPIO Port A (AHB) base: 0x4005.8000 GPIO Port B (APB) base: 0x4000.5000 GPIO Port B (AHB) base: 0x4005.9000 GPIO Port C (APB) base: 0x4000.6000 GPIO Port C (AHB) base: 0x4005.A000 GPIO Port D (APB) base: 0x4000.7000 GPIO Port D (AHB) base: 0x4005.B000 GPIO Port E (APB) base: 0x4002.4000 GPIO Port E (AHB) base: 0x4005.C000 GPIO Port F (APB) base: 0x4002.5000 GPIO Port F (AHB) base: 0x4005.D000 GPIO Port G (APB) base: 0x4002.6000 GPIO Port G (AHB) base: 0x4005.E000 GPIO Port H (APB) base: 0x4002.7000 GPIO Port H (AHB) base: 0x4005.F000 GPIO Port J (APB) base: 0x4003.D000 GPIO Port J (AHB) base: 0x4006.0000 GPIO Port K (AHB) base: 0x4006.1000 Offset 0xFE0

Bit/Field



31:8	reserved	RO	0x0000.00	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
7:0	PID0	RO	0x61	GPIO Peripheral ID Register [7:0] Can be used by software to identify the presence of this peripheral.

Description

Reset


Type

Register 30: GPIO Peripheral Identification 1 (GPIOPeriphID1), offset 0xFE4

The **GPIOPeriphID0**, **GPIOPeriphID1**, **GPIOPeriphID2**, and **GPIOPeriphID3** registers can conceptually be treated as one 32-bit register; each register contains eight bits of the 32-bit register, used by software to identify the peripheral.

GPIO Peripheral Identification 1 (GPIOPeriphID1)

GPIO Port A (APB) base: 0x4000.4000 GPIO Port A (AHB) base: 0x4005.8000 GPIO Port B (APB) base: 0x4000.5000 GPIO Port B (AHB) base: 0x4005.9000 GPIO Port C (APB) base: 0x4000.6000 GPIO Port C (AHB) base: 0x4005.A000 GPIO Port D (APB) base: 0x4000.7000 GPIO Port D (AHB) base: 0x4005.B000 GPIO Port E (APB) base: 0x4002.4000 GPIO Port E (AHB) base: 0x4005.C000 GPIO Port F (APB) base: 0x4002.5000 GPIO Port F (AHB) base: 0x4005.D000 GPIO Port G (APB) base: 0x4002.6000 GPIO Port G (AHB) base: 0x4005.E000 GPIO Port H (APB) base: 0x4002.7000 GPIO Port H (AHB) base: 0x4005.F000 GPIO Port J (APB) base: 0x4003.D000 GPIO Port J (AHB) base: 0x4006.0000 GPIO Port K (AHB) base: 0x4006.1000 Offset 0xFE4 Type RO, reset 0x0000.0000



Bit/Field	Name	Type	Reset	Description
31:8	reserved	RO	0x0000.00	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
7:0	PID1	RO	0x00	GPIO Peripheral ID Register [15:8]
				Can be used by software to identify the presence of this peripheral.

February 20, 2013 697

Register 31: GPIO Peripheral Identification 2 (GPIOPeriphID2), offset 0xFE8

The **GPIOPeriphID0**, **GPIOPeriphID1**, **GPIOPeriphID2**, and **GPIOPeriphID3** registers can conceptually be treated as one 32-bit register; each register contains eight bits of the 32-bit register, used by software to identify the peripheral.


GPIO Peripheral Identification 2 (GPIOPeriphID2)

GPIO Port A (APB) base: 0x4000.4000 GPIO Port A (AHB) base: 0x4005.8000 GPIO Port B (APB) base: 0x4000.5000 GPIO Port B (AHB) base: 0x4005.9000 GPIO Port C (APB) base: 0x4000.6000 GPIO Port C (AHB) base: 0x4005.A000 GPIO Port D (APB) base: 0x4000.7000 GPIO Port D (AHB) base: 0x4005.B000 GPIO Port E (APB) base: 0x4002.4000 GPIO Port E (AHB) base: 0x4005.C000 GPIO Port F (APB) base: 0x4002.5000 GPIO Port F (AHB) base: 0x4005.D000 GPIO Port G (APB) base: 0x4002.6000 GPIO Port G (AHB) base: 0x4005.E000 GPIO Port H (APB) base: 0x4002.7000 GPIO Port H (AHB) base: 0x4005.F000 GPIO Port J (APB) base: 0x4003.D000 GPIO Port J (AHB) base: 0x4006.0000 GPIO Port K (AHB) base: 0x4006.1000 Offset 0xFE8 Type RO, reset 0x0000.0018

Name

Type

Bit/Field



		.) [
31:8	reserved	RO	0x0000.00	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
7:0	PID2	RO	0x18	GPIO Peripheral ID Register [23:16]
				Can be used by software to identify the presence of this peripheral.

Description

Reset

Register 32: GPIO Peripheral Identification 3 (GPIOPeriphID3), offset 0xFEC

The **GPIOPeriphID0**, **GPIOPeriphID1**, **GPIOPeriphID2**, and **GPIOPeriphID3** registers can conceptually be treated as one 32-bit register; each register contains eight bits of the 32-bit register, used by software to identify the peripheral.


GPIO Peripheral Identification 3 (GPIOPeriphID3)

GPIO Port A (APB) base: 0x4000.4000 GPIO Port A (AHB) base: 0x4005.8000 GPIO Port B (APB) base: 0x4000.5000 GPIO Port B (AHB) base: 0x4005.9000 GPIO Port C (APB) base: 0x4000.6000 GPIO Port C (AHB) base: 0x4005.A000 GPIO Port D (APB) base: 0x4000.7000 GPIO Port D (AHB) base: 0x4005.B000 GPIO Port E (APB) base: 0x4002.4000 GPIO Port E (AHB) base: 0x4005.C000 GPIO Port F (APB) base: 0x4002.5000 GPIO Port F (AHB) base: 0x4005.D000 GPIO Port G (APB) base: 0x4002.6000 GPIO Port G (AHB) base: 0x4005.E000 GPIO Port H (APB) base: 0x4002.7000 GPIO Port H (AHB) base: 0x4005.F000 GPIO Port J (APB) base: 0x4003.D000 GPIO Port J (AHB) base: 0x4006.0000 GPIO Port K (AHB) base: 0x4006.1000 Offset 0xFEC Type RO, reset 0x0000.0001

Name

Type

Bit/Field



		71.		
31:8	reserved	RO	0x0000.00	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
7:0	PID3	RO	0x01	GPIO Peripheral ID Register [31:24]
				Can be used by software to identify the presence of this peripheral.

Description

Reset


February 20, 2013 699

Register 33: GPIO PrimeCell Identification 0 (GPIOPCellID0), offset 0xFF0

The **GPIOPCeIIID1**, **GPIOPCeIIID1**, and **GPIOPCeIIID3** registers are four 8-bit wide registers, that can conceptually be treated as one 32-bit register. The register is used as a standard cross-peripheral identification system.

GPIO PrimeCell Identification 0 (GPIOPCellID0)

GPIO Port A (APB) base: 0x4000.4000 GPIO Port A (AHB) base: 0x4005.8000 GPIO Port B (APB) base: 0x4000.5000 GPIO Port B (AHB) base: 0x4005.9000 GPIO Port C (APB) base: 0x4000.6000 GPIO Port C (AHB) base: 0x4005.A000 GPIO Port D (APB) base: 0x4000.7000 GPIO Port D (AHB) base: 0x4005.B000 GPIO Port E (APB) base: 0x4002.4000 GPIO Port E (AHB) base: 0x4005.C000 GPIO Port F (APB) base: 0x4002.5000 GPIO Port F (AHB) base: 0x4005.D000 GPIO Port G (APB) base: 0x4002.6000 GPIO Port G (AHB) base: 0x4005.E000 GPIO Port H (APB) base: 0x4002.7000 GPIO Port H (AHB) base: 0x4005.F000 GPIO Port J (APB) base: 0x4003.D000 GPIO Port J (AHB) base: 0x4006.0000 GPIO Port K (AHB) base: 0x4006.1000 Offset 0xFF0 Type RO, reset 0x0000.000D



Bit/Field	Name	Type	Reset	Description
31:8	reserved	RO	0x0000.00	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
7:0	CID0	RO	0x0D	GPIO PrimeCell ID Register [7:0]


Provides software a standard cross-peripheral identification system.

Register 34: GPIO PrimeCell Identification 1 (GPIOPCellID1), offset 0xFF4

The **GPIOPCeIIID1**, **GPIOPCeIIID1**, and **GPIOPCeIIID3** registers are four 8-bit wide registers, that can conceptually be treated as one 32-bit register. The register is used as a standard cross-peripheral identification system.

GPIO PrimeCell Identification 1 (GPIOPCellID1)

GPIO Port A (APB) base: 0x4000.4000 GPIO Port A (AHB) base: 0x4005.8000 GPIO Port B (APB) base: 0x4000.5000 GPIO Port B (AHB) base: 0x4005.9000 GPIO Port C (APB) base: 0x4000.6000 GPIO Port C (AHB) base: 0x4005.A000 GPIO Port D (APB) base: 0x4000.7000 GPIO Port D (AHB) base: 0x4005.B000 GPIO Port E (APB) base: 0x4002.4000 GPIO Port E (AHB) base: 0x4005.C000 GPIO Port F (APB) base: 0x4002.5000 GPIO Port F (AHB) base: 0x4005.D000 GPIO Port G (APB) base: 0x4002.6000 GPIO Port G (AHB) base: 0x4005.E000 GPIO Port H (APB) base: 0x4002.7000 GPIO Port H (AHB) base: 0x4005.F000 GPIO Port J (APB) base: 0x4003.D000 GPIO Port J (AHB) base: 0x4006.0000 GPIO Port K (AHB) base: 0x4006.1000 Offset 0xFF4 Type RO, reset 0x0000.00F0



Bit/Field	Name	Type	Reset	Description
31:8	reserved	RO	0x0000.00	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
7:0	CID1	RO	0xF0	GPIO PrimeCell ID Register [15:8]

Provides software a standard cross-peripheral identification system.


February 20, 2013 701

Register 35: GPIO PrimeCell Identification 2 (GPIOPCellID2), offset 0xFF8

The **GPIOPCeIIID1**, **GPIOPCeIIID1**, and **GPIOPCeIIID3** registers are four 8-bit wide registers, that can conceptually be treated as one 32-bit register. The register is used as a standard cross-peripheral identification system.

GPIO PrimeCell Identification 2 (GPIOPCellID2)

GPIO Port A (APB) base: 0x4000.4000 GPIO Port A (AHB) base: 0x4005.8000 GPIO Port B (APB) base: 0x4000.5000 GPIO Port B (AHB) base: 0x4005.9000 GPIO Port C (APB) base: 0x4000.6000 GPIO Port C (AHB) base: 0x4005.A000 GPIO Port D (APB) base: 0x4000.7000 GPIO Port D (AHB) base: 0x4005.B000 GPIO Port E (APB) base: 0x4002.4000 GPIO Port E (AHB) base: 0x4005.C000 GPIO Port F (APB) base: 0x4002.5000 GPIO Port F (AHB) base: 0x4005.D000 GPIO Port G (APB) base: 0x4002.6000 GPIO Port G (AHB) base: 0x4005.E000 GPIO Port H (APB) base: 0x4002.7000 GPIO Port H (AHB) base: 0x4005.F000 GPIO Port J (APB) base: 0x4003.D000 GPIO Port J (AHB) base: 0x4006.0000 GPIO Port K (AHB) base: 0x4006.1000 Offset 0xFF8 Type RO, reset 0x0000.0005



Bit/Field	Name	Type	Reset	Description
31:8	reserved	RO	0x0000.00	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
7:0	CID2	RO	0x05	GPIO PrimeCell ID Register [23:16]


Provides software a standard cross-peripheral identification system.

Register 36: GPIO PrimeCell Identification 3 (GPIOPCelIID3), offset 0xFFC

The **GPIOPCeIIID1**, **GPIOPCeIIID1**, and **GPIOPCeIIID3** registers are four 8-bit wide registers, that can conceptually be treated as one 32-bit register. The register is used as a standard cross-peripheral identification system.

GPIO PrimeCell Identification 3 (GPIOPCellID3)

GPIO Port A (APB) base: 0x4000.4000 GPIO Port A (AHB) base: 0x4005.8000 GPIO Port B (APB) base: 0x4000.5000 GPIO Port B (AHB) base: 0x4005.9000 GPIO Port C (APB) base: 0x4000.6000 GPIO Port C (AHB) base: 0x4005.A000 GPIO Port D (APB) base: 0x4000.7000 GPIO Port D (AHB) base: 0x4005.B000 GPIO Port E (APB) base: 0x4002.4000 GPIO Port E (AHB) base: 0x4005.C000 GPIO Port F (APB) base: 0x4002.5000 GPIO Port F (AHB) base: 0x4005.D000 GPIO Port G (APB) base: 0x4002.6000 GPIO Port G (AHB) base: 0x4005.E000 GPIO Port H (APB) base: 0x4002.7000 GPIO Port H (AHB) base: 0x4005.F000 GPIO Port J (APB) base: 0x4003.D000 GPIO Port J (AHB) base: 0x4006.0000 GPIO Port K (AHB) base: 0x4006.1000 Offset 0xFFC Type RO, reset 0x0000.00B1



Bit/Field	Name	Type	Reset	Description
31:8	reserved	RO	0x0000.00	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
7:0	CID3	RO	0xB1	GPIO PrimeCell ID Register [31:24]

Provides software a standard cross-peripheral identification system.

February 20, 2013 703

11 General-Purpose Timers

Programmable timers can be used to count or time external events that drive the Timer input pins. The Stellaris General-Purpose Timer Module (GPTM) contains six 16/32-bit GPTM blocks and six 32/64-bit Wide GPTM blocks. Each 16/32-bit GPTM block provides two 16-bit timers/counters (referred to as Timer A and Timer B) that can be configured to operate independently as timers or event counters, or concatenated to operate as one 32-bit timer or one 32-bit Real-Time Clock (RTC). Each 32/64-bit Wide GPTM block provides 32-bit timers for Timer A and Timer B that can be concatenated to operate as a 64-bit timer. Timers can also be used to trigger μ DMA transfers.

In addition, timers can be used to trigger analog-to-digital conversions (ADC). The ADC trigger signals from all of the general-purpose timers are ORed together before reaching the ADC module, so only one timer should be used to trigger ADC events.

The GPT Module is one timing resource available on the Stellaris microcontrollers. Other timer resources include the System Timer (SysTick) (see 127) and the PWM timer in the PWM modules (see "PWM Timer" on page 1239).

The General-Purpose Timer Module (GPTM) contains six 16/32-bit GPTM blocks and six 32/64-bit Wide GPTM blocks with the following functional options:

- 16/32-bit operating modes:
 - 16- or 32-bit programmable one-shot timer
 - 16- or 32-bit programmable periodic timer
 - 16-bit general-purpose timer with an 8-bit prescaler
 - 32-bit Real-Time Clock (RTC) when using an external 32.768-KHz clock as the input
 - 16-bit input-edge count- or time-capture modes with an 8-bit prescaler
 - 16-bit PWM mode with an 8-bit prescaler and software-programmable output inversion of the PWM signal
- 32/64-bit operating modes:
 - 32- or 64-bit programmable one-shot timer
 - 32- or 64-bit programmable periodic timer
 - 32-bit general-purpose timer with a 16-bit prescaler
 - 64-bit Real-Time Clock (RTC) when using an external 32.768-KHz clock as the input
 - 32-bit input-edge count- or time-capture modes with a16-bit prescaler
 - 32-bit PWM mode with a 16-bit prescaler and software-programmable output inversion of the PWM signal
- Count up or down
- Twelve 16/32-bit Capture Compare PWM pins (CCP)
- Twelve 32/64-bit Capture Compare PWM pins (CCP)

- Daisy chaining of timer modules to allow a single timer to initiate multiple timing events
- Timer synchronization allows selected timers to start counting on the same clock cycle
- ADC event trigger
- User-enabled stalling when the microcontroller asserts CPU Halt flag during debug (excluding RTC mode)
- Ability to determine the elapsed time between the assertion of the timer interrupt and entry into the interrupt service routine
- Efficient transfers using Micro Direct Memory Access Controller (µDMA)
 - Dedicated channel for each timer
 - Burst request generated on timer interrupt

11.1 Block Diagram

In the block diagram, the specific Capture Compare PWM (CCP) pins available depend on the Stellaris device. See Table 11-1 on page 706 for the available CCP pins and their timer assignments.

Figure 11-1. GPTM Module Block Diagram




Table 11-1. Available CCP Pins

Timer	Up/Down Counter	Even CCP Pin	Odd CCP Pin
16/32-Bit Timer 0	Timer A	TOCCPO	-
16/32-Bit Tilliel U	Timer B	-	TOCCP1
16/32-Bit Timer 1	Timer A	T1CCP0	-
16/32-Bit Tilliel 1	Timer B	-	T1CCP1
16/32-Bit Timer 2	Timer A	T2CCP0	-
10/32-bit filliel 2	Timer B	-	T2CCP1
16/22 Dit Timor 2	Timer A	T3CCP0	-
5/32-Bit Timer 3 5/32-Bit Timer 4	Timer B	-	T3CCP1
16/22 Pit Timor 4	Timer A	T4CCP0	-
10/32-bit filllel 4	Timer B	-	T4CCP1
16/32-Bit Timer 5	Timer A	T5CCP0	-
	Timer B	-	T5CCP1
32/64-Bit Wide Timer 0	Timer A	WT0CCP0	-
32/04-bit Wide Timer 0	Timer B	-	WT0CCP1
32/64-Bit Wide Timer 1	Timer A	WT1CCP0	-
32/04-bit Wide Tilliel T	Timer B	-	WT1CCP1
32/64-Bit Wide Timer 2	Timer A	WT2CCP0	-
32/04-bit Wide Tilliel 2	Timer B	-	WT2CCP1
32/64-Bit Wide Timer 3	Timer A	WT3CCP0	-
32/04-bit Wide Timer 3	Timer B	-	WT3CCP1
32/64-Bit Wide Timer 4	Timer A	WT4CCP0	-
32/04-DIL WINE TIME! 4	Timer B	-	WT4CCP1
32/64-Bit Wide Timer 5	Timer A	WT5CCP0	-
32/04-DIL WILLE TITLE! 5	Timer B	-	WT5CCP1

11.2 Signal Description

The following table lists the external signals of the GP Timer module and describes the function of each. The GP Timer signals are alternate functions for some GPIO signals and default to be GPIO signals at reset. The column in the table below titled "Pin Mux/Pin Assignment" lists the possible GPIO pin placements for these GP Timer signals. The AFSEL bit in the **GPIO Alternate Function Select (GPIOAFSEL)** register (page 670) should be set to choose the GP Timer function. The number in parentheses is the encoding that must be programmed into the PMCn field in the **GPIO Port Control (GPIOPCTL)** register (page 688) to assign the GP Timer signal to the specified GPIO port pin. For more information on configuring GPIOs, see "General-Purpose Input/Outputs (GPIOs)" on page 646.

Table 11-2. General-Purpose Timers Signals (100LQFP)

Pin Name	Pin Number	Pin Mux / Pin Assignment	Pin Type	Buffer Type ^a	Description
T0CCP0	40	PF0 (7)	I/O	TTL	16/32-Bit Timer 0 Capture/Compare/PWM 0.
T0CCP1	41	PF1 (7)	I/O	TTL	16/32-Bit Timer 0 Capture/Compare/PWM 1.

Table 11-2. General-Purpose Timers Signals (100LQFP) (continued)

Pin Name	Pin Number	Pin Mux / Pin Assignment	Pin Type	Buffer Type ^a	Description
T1CCP0	42 68 92	PF2 (7) PJ0 (7) PB4 (7)	I/O	TTL	16/32-Bit Timer 1 Capture/Compare/PWM 0.
T1CCP1	43 69 91	PF3 (7) PJ1 (7) PB5 (7)	I/O	TTL	16/32-Bit Timer 1 Capture/Compare/PWM 1.
T2CCP0	11 39 70	PJ2 (7) PF4 (7) PB0 (7)	I/O	TTL	16/32-Bit Timer 2 Capture/Compare/PWM 0.
T2CCP1	37 71	PF5 (7) PB1 (7)	I/O	TTL	16/32-Bit Timer 2 Capture/Compare/PWM 1.
T3CCP0	36 72	PF6 (7) PB2 (7)	I/O	TTL	16/32-Bit Timer 3 Capture/Compare/PWM 0.
T3CCP1	58 73	PF7 (7) PB3 (7)	I/O	TTL	16/32-Bit Timer 3 Capture/Compare/PWM 1.
T4CCP0	62 85	PG0 (7) PC0 (7)	I/O	TTL	16/32-Bit Timer 4 Capture/Compare/PWM 0.
T4CCP1	61 84	PG1 (7) PC1 (7)	I/O	TTL	16/32-Bit Timer 4 Capture/Compare/PWM 1.
T5CCP0	60 83	PG2 (7) PC2 (7)	I/O	TTL	16/32-Bit Timer 5 Capture/Compare/PWM 0.
T5CCP1	59 82	PG3 (7) PC3 (7)	I/O	TTL	16/32-Bit Timer 5 Capture/Compare/PWM 1.
WT0CCP0	25 74	PC4 (7) PG4 (7)	I/O	TTL	32/64-Bit Wide Timer 0 Capture/Compare/PWM 0.
WT0CCP1	24 75	PC5 (7) PG5 (7)	I/O	TTL	32/64-Bit Wide Timer 0 Capture/Compare/PWM 1.
WT1CCP0	23 87	PC6 (7) PG6 (7)	I/O	TTL	32/64-Bit Wide Timer 1 Capture/Compare/PWM 0.
WT1CCP1	22 88	PC7 (7) PG7 (7)	I/O	TTL	32/64-Bit Wide Timer 1 Capture/Compare/PWM 1.
WT2CCP0	1 16	PD0 (7) PH0 (7)	I/O	TTL	32/64-Bit Wide Timer 2 Capture/Compare/PWM 0.
WT2CCP1	2 17	PD1 (7) PH1 (7)	I/O	TTL	32/64-Bit Wide Timer 2 Capture/Compare/PWM 1.
WT3CCP0	3 79	PD2 (7) PH4 (7)	I/O	TTL	32/64-Bit Wide Timer 3 Capture/Compare/PWM 0.
WT3CCP1	4 78	PD3 (7) PH5 (7)	I/O	TTL	32/64-Bit Wide Timer 3 Capture/Compare/PWM 1.
WT4CCP0	77 97	PH6 (7) PD4 (7)	I/O	TTL	32/64-Bit Wide Timer 4 Capture/Compare/PWM 0.
WT4CCP1	76 98	PH7 (7) PD5 (7)	I/O	TTL	32/64-Bit Wide Timer 4 Capture/Compare/PWM 1.
WT5CCP0	18 99	PH2 (7) PD6 (7)	I/O	TTL	32/64-Bit Wide Timer 5 Capture/Compare/PWM 0.
WT5CCP1	19 100	PH3 (7) PD7 (7)	I/O	TTL	32/64-Bit Wide Timer 5 Capture/Compare/PWM 1.

a. The TTL designation indicates the pin has TTL-compatible voltage levels.

11.3 Functional Description

The main components of each GPTM block are two free-running up/down counters (referred to as Timer A and Timer B), two prescaler registers, two match registers, two prescaler match registers, two shadow registers, and two load/initialization registers and their associated control functions. The exact functionality of each GPTM is controlled by software and configured through the register interface. Timer A and Timer B can be used individually, in which case they have a 16-bit counting range for the 16/32-bit GPTM blocks and a 32-bit counting range for 32/64-bit Wide GPTM blocks. In addition, Timer A and Timer B can be concatenated to provide a 32-bit counting range for the 16/32-bit GPTM blocks and a 64-bit counting range for the 32/64-bit Wide GPTM blocks. Note that the prescaler can only be used when the timers are used individually.

The available modes for each GPTM block are shown in Table 11-3 on page 708. Note that when counting down in one-shot or periodic modes, the prescaler acts as a true prescaler and contains the least-significant bits of the count. When counting up in one-shot or periodic modes, the prescaler acts as a timer extension and holds the most-significant bits of the count. In input edge count, input edge time and PWM mode, the prescaler always acts as a timer extension, regardless of the count direction.

		Count	Cour	nter Size	Prescaler Size ^a		Prescaler Behavior
Mode	Timer Use	Direction	16/32-bit GPTM	32/64-bit Wide GPTM	16/32-bit GPTM	32/64-bit Wide GPTM	(Count Direction)
One-shot	Individual	Up or Down	16-bit	32-bit	8-bit	16-bit	Timer Extension (Up), Prescaler (Down)
	Concatenated	Up or Down	32-bit	64-bit	-	-	N/A
Periodic	Individual	Up or Down	16-bit	32-bit	8-bit	16-bit	Timer Extension (Up), Prescaler (Down)
	Concatenated	Up or Down	32-bit	64-bit	-	-	N/A
RTC	Concatenated	Up	32-bit	64-bit	-	-	N/A
Edge Count	Individual	Up or Down	16-bit	32-bit	8-bit	16-bit	Timer Extension (Both)
Edge Time	Individual	Up or Down	16-bit	32-bit	8-bit	16-bit	Timer Extension (Both)
PWM	Individual	Down	16-bit	32-bit	8-bit	16-bit	Timer Extension

a. The prescaler is only available when the timers are used individually

Software configures the GPTM using the **GPTM Configuration (GPTMCFG)** register (see page 727), the **GPTM Timer A Mode (GPTMTAMR)** register (see page 729), and the **GPTM Timer B Mode (GPTMTBMR)** register (see page 733). When in one of the concatentated modes, Timer A and Timer B can only operate in one mode. However, when configured in an individual mode, Timer A and Timer B can be independently configured in any combination of the individual modes.

11.3.1 GPTM Reset Conditions

After reset has been applied to the GPTM module, the module is in an inactive state, and all control registers are cleared and in their default states. Counters Timer A and Timer B are initialized to all 1s, along with their corresponding registers:

- Load Registers:
 - GPTM Timer A Interval Load (GPTMTAILR) register (see page 756)

- GPTM Timer B Interval Load (GPTMTBILR) register (see page 757)
- Shadow Registers:
 - **GPTM Timer A Value (GPTMTAV)** register (see page 766)
 - GPTM Timer B Value (GPTMTBV) register (see page 767)

The following prescale counters are initialized to all 0s:

- GPTM Timer A Prescale (GPTMTAPR) register (see page 760)
- GPTM Timer B Prescale (GPTMTBPR) register (see page 761)
- GPTM Timer A Prescale Snapshot (GPTMTAPS) register (see page 769)
- **GPTM Timer B Prescale Snapshot (GPTMTBPS)** register (see page 770)
- GPTM Timer A Prescale Value (GPTMTAPV) register (see page 771)
- GPTM Timer B Prescale Value (GPTMTBPV) register (see page 772)

11.3.2 Timer Modes

This section describes the operation of the various timer modes. When using Timer A and Timer B in concatenated mode, only the Timer A control and status bits must be used; there is no need to use Timer B control and status bits. The GPTM is placed into individual/split mode by writing a value of 0x4 to the **GPTM Configuration (GPTMCFG)** register (see page 727). In the following sections, the variable "n" is used in bit field and register names to imply either a Timer A function or a Timer B function. Throughout this section, the timeout event in down-count mode is 0x0 and in up-count mode is the value in the **GPTM Timer n Interval Load (GPTMTnILR)** and the optional **GPTM Timer n Prescale (GPTMTnPR)** registers.

11.3.2.1 One-Shot/Periodic Timer Mode

The selection of one-shot or periodic mode is determined by the value written to the TnMR field of the **GPTM Timer n Mode (GPTMTnMR)** register (see page 729). The timer is configured to count up or down using the TnCDIR bit in the **GPTMTnMR** register.

When software sets the TnEN bit in the **GPTM Control (GPTMCTL)** register (see page 737), the timer begins counting up from 0x0 or down from its preloaded value. Alternatively, if the TnWOT bit is set in the **GPTMTnMR** register, once the TnEN bit is set, the timer waits for a trigger to begin counting (see "Wait-for-Trigger Mode" on page 718). Table 11-4 on page 709 shows the values that are loaded into the timer registers when the timer is enabled.

Table 11-4. Counter Values When the Timer is Enabled in Periodic or One-Shot Modes

Register	Count Down Mode	Count Up Mode
GPTMTnR	GPTMTnILR	0x0
GPTMTnV	GPTMTnILR	0x0
GPTMTnPS	GPTMTnPR in individual mode; not available in concatenated mode	0x0 in individual mode; not available in concatenated mode
GPTMTnPV	GPTMTnPR in individual mode; not available in concatenated mode	0x0 in individual mode; not available in concatenated mode

When the timer is counting down and it reaches the timeout event (0x0), the timer reloads its start value from the **GPTMTnILR** and the **GPTMTnPR** registers on the next cycle. When the timer is counting up and it reaches the timeout event (the value in the **GPTMTnILR** and the optional **GPTMTnPR** registers), the timer reloads with 0x0. If configured to be a one-shot timer, the timer stops counting and clears the TnEN bit in the **GPTMCTL** register. If configured as a periodic timer, the timer starts counting again on the next cycle.

In periodic, snap-shot mode (TnMR field is 0x2 and the TnSNAPS bit is set in the **GPTMTnMR** register), the value of the timer at the time-out event is loaded into the **GPTMTnR** register and the value of the prescaler is loaded into the **GPTMTnPS** register. The free-running counter value is shown in the **GPTMTnV** register and the free-running prescaler value is shown in the **GPTMTnPV** register. In this manner, software can determine the time elapsed from the interrupt assertion to the ISR entry by examining the snapshot values and the current value of the free-running timer. Snapshot mode is not available when the timer is configured in one-shot mode.

In addition to reloading the count value, the GPTM generates interrupts and triggers when it reaches the time-out event. The GPTM sets the TnTORIS bit in the GPTM Raw Interrupt Status (GPTMRIS) register (see page 748), and holds it until it is cleared by writing the GPTM Interrupt Clear (GPTMICR) register (see page 754). If the time-out interrupt is enabled in the GPTM Interrupt Mask (GPTMIMR) register (see page 745), the GPTM also sets the TnTOMIS bit in the GPTM Masked Interrupt Status (GPTMMIS) register (see page 751). The time-out interrupt can be disabled entirely by setting the TACINTD bit in the GPTM Timer n Mode (GPTMTnMR) register. In this case, the TnTORIS bit does not even set in the GPTMRIS register.

By setting the \mathtt{TnMIE} bit in the **GPTMTnMR** register, an interrupt condition can also be generated when the Timer value equals the value loaded into the **GPTM Timer n Match (GPTMTnMATCHR)** and **GPTM Timer n Prescale Match (GPTMTnPMR)** registers. This interrupt has the same status, masking, and clearing functions as the time-out interrupt, but uses the match interrupt bits instead (for example, the raw interrupt status is monitored via \mathtt{TnMRIS} bit in the **GPTM Raw Interrupt Status (GPTMRIS)** register). Note that the interrupt status bits are not updated by the hardware unless the \mathtt{TnMIE} bit in the **GPTMTnMR** register is set, which is different than the behavior for the time-out interrupt. The ADC trigger is enabled by setting the \mathtt{TnOTE} bit in **GPTMCTL**. The $\mathtt{\muDMA}$ trigger is enabled by configuring and enabling the appropriate $\mathtt{\muDMA}$ channel. See "Channel Configuration" on page 586.

If software updates the **GPTMTnILR** or the **GPTMTnPR** register while the counter is counting down, the counter loads the new value on the next clock cycle and continues counting from the new value if the <code>TnILD</code> bit in the **GPTMTnMR** register is clear. If the <code>TnILD</code> bit is set, the counter loads the new value after the next timeout. If software updates the **GPTMTnILR** or the **GPTMTnPR** register while the counter is counting up, the timeout event is changed on the next cycle to the new value. If software updates the **GPTM Timer n Value (GPTMTnV)** register while the counter is counting up or down, the counter loads the new value on the next clock cycle and continues counting from the new value. If software updates the **GPTMTnMATCHR** or the **GPTMTnPMR** registers, the new values are reflected on the next clock cycle if the <code>TnMRSU</code> bit in the **GPTMTnMR** register is clear. If the <code>TnMRSU</code> bit is set, the new value will not take effect until the next timeout.

When using a 32/64-bit wide timer block in a 64-bit mode, certain registers must be accessed in the manner described in "Accessing Concatenated 32/64-Bit Wide GPTM Register Values" on page 720.

If the TnSTALL bit in the **GPTMCTL** register is set, the timer freezes counting while the processor is halted by the debugger. The timer resumes counting when the processor resumes execution.

The following table shows a variety of configurations for a 16-bit free-running timer while using the prescaler. All values assume an 80-MHz clock with Tc=12.5 ns (clock period). The prescaler can only be used when a 16/32-bit timer is configured in 16-bit mode and when a 32/64-bit timer is configured in 32-bit mode.

Table 11-5. 16-Bit Timer With Prescaler Configurations

Prescale (8-bit value)	# of Timer Clocks (Tc) ^a	Max Time	Units
0000000	1	0.8192	ms
0000001	2	1.6384	ms
0000010	3	2.4576	ms
11111101	254	208.0768	ms
11111110	255	208.896	ms
11111111	256	209.7152	ms

a. Tc is the clock period.

The following table shows a variety of configurations for a 32-bit free-running timer using the prescaler while configured in 32/64-bit mode. All values assume an 80-MHz clock with Tc=12.5 ns (clock period).

Table 11-6. 32-Bit Timer (configured in 32/64-bit mode) With Prescaler Configurations

Prescale (16-bit value)	# of Timer Clocks (Tc) ^a	Max Time	Units
0x0000	1	53.687	S
0x0001	2	107.374	s
0x0002	3	214.748	s
0xFFFD	65534	0.879	10 ⁶ s
0xFFFE	65535	1.759	10 ⁶ s
0xFFFF	65536	3.518	10 ⁶ s

a. Tc is the clock period.

11.3.2.2 Real-Time Clock Timer Mode

In Real-Time Clock (RTC) mode, the concatenated versions of the Timer A and Timer B registers are configured as an up-counter. When RTC mode is selected for the first time after reset, the counter is loaded with a value of 0x1. All subsequent load values must be written to the **GPTM Timer n Interval Load (GPTMTnILR)** registers (see page 756). If the **GPTMTnILR** register is loaded with a new value, the counter begins counting at that value and rolls over at the fixed value of 0xFFFFFFF. Table 11-7 on page 711 shows the values that are loaded into the timer registers when the timer is enabled.

Table 11-7. Counter Values When the Timer is Enabled in RTC Mode

Register	Count Down Mode	Count Up Mode
GPTMTnR	Not available	0x1
GPTMTnV	Not available	0x1
GPTMTnPS	Not available	Not available
GPTMTnPV	Not available	Not available

The input clock on a CCP0 input is required to be 32.768 KHz in RTC mode. The clock signal is then divided down to a 1-Hz rate and is passed along to the input of the counter.

When software writes the TAEN bit in the **GPTMCTL** register, the counter starts counting up from its preloaded value of 0x1. When the current count value matches the preloaded value in the


GPTMTnMATCHR registers, the GPTM asserts the RTCRIS bit in **GPTMRIS** and continues counting until either a hardware reset, or it is disabled by software (clearing the TAEN bit). When the timer value reaches the terminal count, the timer rolls over and continues counting up from 0x0. If the RTC interrupt is enabled in **GPTMIMR**, the GPTM also sets the RTCMIS bit in **GPTMMIS** and generates a controller interrupt. The status flags are cleared by writing the RTCCINT bit in **GPTMICR**.

In this mode, the **GPTMTnR** and **GPTMTnV** registers always have the same value.

When using a 32/64-bit wide timer block in a RTC mode, certain registers must be accessed in the manner described in "Accessing Concatenated 32/64-Bit Wide GPTM Register Values" on page 720.

The value of the RTC predivider can be read in the **GPTM RTC Predivide (GPTMRTCPD)** register. To ensure that the RTC value is coherent, software should follow the process detailed in Figure 11-2 on page 712.

Figure 11-2. Reading the RTC Value



In addition to generating interrupts, the RTC can generate a μ DMA trigger. The μ DMA trigger is enabled by configuring and enabling the appropriate μ DMA channel. See "Channel Configuration" on page 586.

If the TASTALL bit in the **GPTMCTL** register is set, the timer does not freeze when the processor is halted by the debugger if the RTCEN bit is set in **GPTMCTL**.

11.3.2.3 Input Edge-Count Mode

Note:

For rising-edge detection, the input signal must be High for at least two system clock periods following the rising edge. Similarly, for falling-edge detection, the input signal must be Low for at least two system clock periods following the falling edge. Based on this criteria, the maximum input frequency for edge detection is 1/4 of the system frequency.

In Edge-Count mode, the timer is configured as a 24-bit or 48-bit up- or down-counter including the optional prescaler with the upper count value stored in the GPTM Timer n Prescale (GPTMTnPR) register and the lower bits in the GPTMTnR register. In this mode, the timer is capable of capturing three types of events: rising edge, falling edge, or both. To place the timer in Edge-Count mode, the TnCMR bit of the GPTMTnMR register must be cleared. The type of edge that the timer counts is determined by the TnEVENT fields of the GPTMCTL register. During initialization in down-count mode, the GPTMTnMATCHR and GPTMTnPMR registers are configured so that the difference between the value in the GPTMTnILR and GPTMTnPR registers and the GPTMTnMATCHR and GPTMTnPMR registers equals the number of edge events that must be counted. In up-count mode, the timer counts from 0x0 to the value in the GPTMTnMATCHR and GPTMTnPMR registers. Note that when executing an up-count, that the value of GPTMTnPR and GPTMTnILR must be greater than the value of GPTMTnPMR and GPTMTnPMR and GPTMTnILR must be greater than the value of GPTMTnPMR and GPTMTnMATCHR. Table 11-8 on page 713 shows the values that are loaded into the timer registers when the timer is enabled.

Table 11-8. Counter Values When the Timer is Enabled in Input Edge-Count Mode

Register	Count Down Mode	Count Up Mode
GPTMTnR	GPTMTnlLR	0x0
GPTMTnV	GPTMTnlLR	0x0
GPTMTnPS	GPTMTnPR	0x0
GPTMTnPV	GPTMTnPR	0x0

When software writes the TnEN bit in the GPTM Control (GPTMCTL) register, the timer is enabled for event capture. Each input event on the CCP pin decrements or increments the counter by 1 until the event count matches GPTMTnMATCHR and GPTMTnPMR. When the counts match, the GPTM asserts the CnMRIS bit in the GPTM Raw Interrupt Status (GPTMRIS) register, and holds it until it is cleared by writing the GPTM Interrupt Clear (GPTMICR) register. If the capture mode match interrupt is enabled in the GPTM Interrupt Mask (GPTMIMR) register, the GPTM also sets the CnMMIS bit in the GPTM Masked Interrupt Status (GPTMMIS) register. In this mode, the GPTMTnR and GPTMTnPS registers hold the count of the input events while the GPTMTnV and GPTMTnPV registers hold the free-running timer value and the free-running prescaler value.

In addition to generating interrupts, an ADC and/or a μ DMA trigger can be generated. The ADC trigger is enabled by setting the TnOTE bit in **GPTMCTL**. The μ DMA trigger is enabled by configuring and enabling the appropriate μ DMA channel. See "Channel Configuration" on page 586.

After the match value is reached in down-count mode, the counter is then reloaded using the value in **GPTMTnILR** and **GPTMTnPR** registers, and stopped because the GPTM automatically clears the TnEN bit in the **GPTMCTL** register. Once the event count has been reached, all further events are ignored until TnEN is re-enabled by software. In up-count mode, the timer is reloaded with 0x0 and continues counting.

Figure 11-3 on page 714 shows how Input Edge-Count mode works. In this case, the timer start value is set to **GPTMTnILR** =0x000A and the match value is set to **GPTMTnMATCHR** =0x0006 so that four edge events are counted. The counter is configured to detect both edges of the input signal.

Note that the last two edges are not counted because the timer automatically clears the ${\tt TnEN}$ bit after the current count matches the value in the **GPTMTnMATCHR** register.




Figure 11-3. Input Edge-Count Mode Example, Counting Down

11.3.2.4 **Input Edge-Time Mode**

TnV

TnPS

TnPV

For rising-edge detection, the input signal must be High for at least two system clock periods following the rising edge. Similarly, for falling edge detection, the input signal must be Low for at least two system clock periods following the falling edge. Based on this criteria, the maximum input frequency for edge detection is 1/4 of the system frequency.

In Edge-Time mode, the timer is configured as a 24-bit or 48-bit up- or down-counter including the optional prescaler with the upper timer value stored in the GPTMTnPR register and the lower bits in the GPTMTnILR register. In this mode, the timer is initialized to the value loaded in the GPTMTnILR and GPTMTnPR registers when counting down and 0x0 when counting up. The timer is capable of capturing three types of events: rising edge, falling edge, or both. The timer is placed into Edge-Time mode by setting the TnCMR bit in the GPTMTnMR register, and the type of event that the timer

	captures is determined by the Tnevent fields of the GPTMCTL register. Table 11-9 on page 714 shows the values that are loaded into the timer registers when the timer is enabled.		
Table 11-9. Counter Values When the Timer is Enabled in Input Event-Count Mode			
	Register	Count Down Mode	Count Up Mode
	TnR	GPTMTnILR	0x0

GPTMTnILR

GPTMTnPR

GPTMTnPR

0x0

0x0

0x0

When software writes the TnEN bit in the **GPTMCTL** register, the timer is enabled for event capture. When the selected input event is detected, the current timer counter value is captured in the GPTMTnR and GPTMTnPS registers and is available to be read by the microcontroller. The GPTM then asserts the Cneris bit in the GPTM Raw Interrupt Status (GPTMRIS) register, and holds it until it is cleared by writing the GPTM Interrupt Clear (GPTMICR) register. If the capture mode event interrupt is enabled in the GPTM Interrupt Mask (GPTMIMR) register, the GPTM also sets the CnEMIS bit in the GPTM Masked Interrupt Status (GPTMMIS) register. In this mode, the

GPTMTnR and **GPTMTnPS**registers hold the time at which the selected input event occurred while the **GPTMTnV** and **GPTMTnPV** registers hold the free-running timer value and the free-running prescaler value. These registers can be read to determine the time that elapsed between the interrupt assertion and the entry into the ISR.

In addition to generating interrupts, an ADC and/or a μ DMA trigger can be generated. The ADC trigger is enabled by setting the <code>TnOTE</code> bit in **GPTMCTL**. The μ DMA trigger is enabled by configuring the appropriate μ DMA channel. See "Channel Configuration" on page 586.

After an event has been captured, the timer does not stop counting. It continues to count until the TnEN bit is cleared. When the timer reaches the timeout value, it is reloaded with 0x0 in up-count mode and the value from the **GPTMTnILR** and **GPTMTnPR** registers in down-count mode.

Figure 11-4 on page 715 shows how input edge timing mode works. In the diagram, it is assumed that the start value of the timer is the default value of 0xFFFF, and the timer is configured to capture rising edge events.

Each time a rising edge event is detected, the current count value is loaded into the **GPTMTnR** and **GPTMTnPS** registers, and is held there until another rising edge is detected (at which point the new count value is loaded into the **GPTMTnR** and **GPTMTnPS** registers).




Figure 11-4. 16-Bit Input Edge-Time Mode Example

Note: When operating in Edge-time mode, the counter uses a modulo 2^{24} count if prescaler is enabled or 2^{16} , if not. If there is a possibility the edge could take longer than the count, then another timer can be implemented to ensure detection of the missed edge.

11.3.2.5 PWM Mode

The GPTM supports a simple PWM generation mode. In PWM mode, the timer is configured as a 24-bit or 48-bit down-counter with a start value (and thus period) defined by the **GPTMTnILR** and **GPTMTnPR** registers. In this mode, the PWM frequency and period are synchronous events and therefore guaranteed to be glitch free. PWM mode is enabled with the **GPTMTnMR** register by setting the TnAMS bit to 0x1, the TnCMR bit to 0x0, and the TnMR field to 0x2. Table 11-10 on page 716 shows the values that are loaded into the timer registers when the timer is enabled.

Table 11-10. Counter Values When the Timer is Enabled in PWM Mode

Register	Count Down Mode	Count Up Mode
GPTMTnR	GPTMTnlLR	Not available
GPTMTnV	GPTMTnlLR	Not available
GPTMTnPS	GPTMTnPR	Not available
GPTMTnPV	GPTMTnPR	Not available

When software writes the TnEN bit in the **GPTMCTL** register, the counter begins counting down until it reaches the 0x0 state. Alternatively, if the TnWOT bit is set in the **GPTMTnMR** register, once the TnEN bit is set, the timer waits for a trigger to begin counting (see "Wait-for-Trigger Mode" on page 718). On the next counter cycle in periodic mode, the counter reloads its start value from the **GPTMTnILR** and **GPTMTnPR** registers and continues counting until disabled by software clearing the TnEN bit in the **GPTMCTL** register. The timer is capable of generating interrupts based on three types of events: rising edge, falling edge, or both. The event is configured by the TnEVENT field of the **GPTMCTL** register, and the interrupt is enabled by setting the TnPWMIE bit in the **GPTMTnMR** register. When the event occurs, the CnERIS bit is set in the **GPTM Raw Interrupt Status (GPTMRIS)** register, and holds it until it is cleared by writing the **GPTM Interrupt Clear (GPTMICR)** register. If the capture mode event interrupt is enabled in the **GPTM Interrupt Mask (GPTMIMR)** register, the GPTM also sets the CnEMIS bit in the **GPTM Masked Interrupt Status (GPTMMIS)** register. Note that the interrupt status bits are not updated unless the TnPWMIE bit is set.

In this mode, the **GPTMTnR** and **GPTMTnV** registers always have the same value, as do the **GPTMPnPS** and the **GPTMTnPV** registers.

The output PWM signal asserts when the counter is at the value of the **GPTMTnILR** and **GPTMTnPR** registers (its start state), and is deasserted when the counter value equals the value in the **GPTMTnMATCHR** and **GPTMTnPMR** registers. Software has the capability of inverting the output PWM signal by setting the TnPWML bit in the **GPTMCTL** register.

Note: If PWM output inversion is enabled, edge detection interrupt behavior is reversed. Thus, if a positive-edge interrupt trigger has been set and the PWM inversion generates a positive edge, no event-trigger interrupt asserts. Instead, the interrupt is generated on the negative edge of the PWM signal.

Figure 11-5 on page 717 shows how to generate an output PWM with a 1-ms period and a 66% duty cycle assuming a 50-MHz input clock and **TnPWML** =0 (duty cycle would be 33% for the **TnPWML** =1 configuration). For this example, the start value is **GPTMTnILR**=0xC350 and the match value is **GPTMTnMATCHR**=0x411A.




Figure 11-5. 16-Bit PWM Mode Example

When synchronizing the timers using the **GPTMSYNC** register, the timer must be properly configured to avoid glitches on the CCP outputs. Both the PLO and the MRSU bits must be set in the **GPTMTnMR** register. Figure 11-6 on page 717 shows how the CCP output operates when the PLO and MRSU bits are set and the **GPTMTnMATCHR** value is greater than the **GPTMTnILR** value.






Figure 11-7 on page 718 shows how the CCP output operates when the PLO and MRSU bits are set and the **GPTMTnMATCHR** value is the same as the **GPTMTnILR** value. In this situation, if the **PLO** bit is 0, the CCP signal goes high when the **GPTMTnILR** value is loaded and the match would be essentially ignored.

February 20, 2013 717




Figure 11-7. CCP Output, GPTMTnMATCHR = GPTMTnlLR

Figure 11-8 on page 718 shows how the CCP output operates when the PLO and MRSU bits are set and the **GPTMTnILR** is greater than the **GPTMTnMATCHR** value.





Figure 11-8. CCP Output, GPTMTnILR > GPTMTnMATCHR

11.3.3 Wait-for-Trigger Mode

The Wait-for-Trigger mode allows daisy chaining of the timer modules such that once configured, a single timer can initiate mulitple timing events using the Timer triggers. Wait-for-Trigger mode is enabled by setting the TnWOT bit in the **GPTMTnMR** register. When the TnWOT bit is set, Timer N+1 does not begin counting until the timer in the previous position in the daisy chain (Timer N) reaches its time-out event. The daisy chain is configured such that GPTM1 always follows GPTM0, GPTM2 follows GPTM1, and so on. If Timer A is configured as a 32-bit (16/32-bit mode) or 64-bit (32/64-bit wide mode) timer (controlled by the GPTMCFG field in the **GPTMCFG** register), it triggers Timer A in the next module. If Timer A is configured as a 16-bit (16/32-bit mode) or 32-bit (32/64-bit wide mode) timer, it triggers Timer B in the same module, and Timer B triggers Timer A in the next module. Care must be taken that the TAWOT bit is never set in GPTM0. Figure 11-9 on page 719 shows how the GPTMCFG bit affects the daisy chain. This function is valid for one-shot, periodic, and PWM modes.

Figure 11-9. Timer Daisy Chain



11.3.4 Synchronizing GP Timer Blocks

The **GPTM Synchronizer Control (GPTMSYNC)** register in the GPTM0 block can be used to synchronize selected timers to begin counting at the same time. Setting a bit in the **GPTMSYNC** register causes the associated timer to perform the actions of a timeout event. An interrupt is not generated when the timers are synchronized. If a timer is being used in concatenated mode, only the bit for Timer A must be set in the **GPTMSYNC** register.

Note: All timers must use the same clock source for this feature to work correctly.

Table 11-11 on page 719 shows the actions for the timeout event performed when the timers are synchronized in the various timer modes.

Table 11-11. Timeout Actions for GPTM Modes

Mode	Count Dir	Time Out Action
32- and 64-bit One-Shot (concatenated timers)	_	N/A
32- and 64-bit Periodic	Down	Count value = ILR
(concatenated timers)	Up	Count value = 0
32- and 64-bit RTC (concatenated timers)	Up	Count value = 0
16- and 32- bit One Shot (individual/split timers)	_	N/A
16- and 32- bit Periodic	Down	Count value = ILR
(individual/split timers)	Up	Count value = 0
16- and 32- bit	Down	Count value = ILR
Edge-Count (individual/split timers)	Up	Count value = 0
16- and 32- bit	Down	Count value = ILR
Edge-Time (individual/split timers)	Up	Count value = 0
16- and 32-bit PWM	Down	Count value = ILR

11.3.5 DMA Operation

The timers each have a dedicated µDMA channel and can provide a request signal to the µDMA controller. The request is a burst type and occurs whenever a timer raw interrupt condition occurs.

The arbitration size of the μ DMA transfer should be set to the amount of data that should be transferred whenever a timer event occurs.

For example, to transfer 256 items, 8 items at a time every 10 ms, configure a timer to generate a periodic timeout at 10 ms. Configure the μ DMA transfer for a total of 256 items, with a burst size of 8 items. Each time the timer times out, the μ DMA controller transfers 8 items, until all 256 items have been transferred.

No other special steps are needed to enable Timers for μ DMA operation. Refer to "Micro Direct Memory Access (μ DMA)" on page 582 for more details about programming the μ DMA controller.

11.3.6 Accessing Concatenated 16/32-Bit GPTM Register Values

The GPTM is placed into concatenated mode by writing a 0x0 or a 0x1 to the GPTMCFG bit field in the **GPTM Configuration (GPTMCFG)** register. In both configurations, certain 16/32-bit GPTM registers are concatenated to form pseudo 32-bit registers. These registers include:

- GPTM Timer A Interval Load (GPTMTAILR) register [15:0], see page 756
- GPTM Timer B Interval Load (GPTMTBILR) register [15:0], see page 757
- **GPTM Timer A (GPTMTAR)** register [15:0], see page 764
- **GPTM Timer B (GPTMTBR)** register [15:0], see page 765
- GPTM Timer A Value (GPTMTAV) register [15:0], see page 766
- GPTM Timer B Value (GPTMTBV) register [15:0], see page 767
- GPTM Timer A Match (GPTMTAMATCHR) register [15:0], see page 758
- GPTM Timer B Match (GPTMTBMATCHR) register [15:0], see page 759

In the 32-bit modes, the GPTM translates a 32-bit write access to **GPTMTAILR** into a write access to both **GPTMTAILR** and **GPTMTBILR**. The resulting word ordering for such a write operation is:

```
GPTMTBILR[15:0]:GPTMTAILR[15:0]
```

Likewise, a 32-bit read access to **GPTMTAR** returns the value:

```
GPTMTBR[15:0]:GPTMTAR[15:0]
```

A 32-bit read access to **GPTMTAV** returns the value:

```
GPTMTBV[15:0]:GPTMTAV[15:0]
```

11.3.7 Accessing Concatenated 32/64-Bit Wide GPTM Register Values

On the 32/64-bit wide GPTM blocks, concatenated register values (64-bits and 48-bits) are not readily available as the bit width for these accesses is greater than the bus width of the processor core. In the concatenated timer modes and the individual timer modes when using the prescaler, software must perform atomic accesses for the value to be coherent. When reading timer values that are greater than 32 bits, software should follow these steps:

- 1. Read the appropriate Timer B register or prescaler register.
- 2. Read the corresponding Timer A register.

- 3. Re-read the Timer B register or prescaler register.
- **4.** Compare the Timer B or prescaler values from the first and second reads. If they are the same, the timer value is coherent. If they are not the same, repeat steps 1-4 once more so that they are the same.

The following pseudo code illustrates this process:

```
high = timer_high;
low = timer_low;
if (high != timer_high); //low overflowed into high
{
    high = timer_high;
    low = timer_low;
}
```

The registers that must be read in this manner are shown below:

- 64-bit reads
 - GPTMTAV and GPTMTBV
 - GPTMTAR and GPTMTBR
- 48-bit reads
 - GPTMTAR and GPTMTAPS
 - GPTMTBR and GPTMTBPS
 - GPTMTAV and GPTMTAPV
 - GPTMTBV and GPTMTBPV

Similarly, write accesses must also be performed by writing the upper bits prior to writing the lower bits as follows:

- 1. Write the appropriate Timer B register or prescaler register.
- **2.** Write the corresponding Timer A register.

The registers that must be written in this manner are shown below:

- 64-bit writes
 - GPTMTAV and GPTMTBV
 - GPTMTAMATCHR and GPTMTBMATCHR
 - GPTMTAILR and GPTMTBILR

- 48-bit writes
 - GPTMTAV and GPTMTAPV
 - GPTMTBV and GPTMTBPV
 - GPTMTAMATCHR and GPTMTAPMR
 - GPTMTBMATCHR and GPTMTBPMR
 - GPTMTAILR and GPTMTAPR
 - GPTMTBILR and GPTMTBPR

When writing a 64-bit value, If there are two consecutive writes to any of the registers listed above under the "64-bit writes" heading, whether the register is in Timer A or Timer B, or if a register Timer A is written prior to writing the corresponding register in Timer B, then an error is reported using the WUERIS bit in the **GPTMRIS** register. This error can be promoted to interrupt if it is not masked. Note that this error is not reported for the prescaler registers because use of the prescaler is optional. As a result, programmers must take care to follow the protocol outlined above.

11.4 Initialization and Configuration

To use a GPTM, the appropriate TIMERn bit must be set in the **RCGCTIMER** or **RCGCWTIMER** register (see page 328 and page 348). If using any CCP pins, the clock to the appropriate GPIO module must be enabled via the **RCGCGPIO** register (see page 330). To find out which GPIO port to enable, refer to Table 23-4 on page 1358. Configure the PMCn fields in the **GPIOPCTL** register to assign the CCP signals to the appropriate pins (see page 688 and Table 23-5 on page 1367).

This section shows module initialization and configuration examples for each of the supported timer modes.

11.4.1 One-Shot/Periodic Timer Mode

The GPTM is configured for One-Shot and Periodic modes by the following sequence:

- 1. Ensure the timer is disabled (the TnEN bit in the **GPTMCTL** register is cleared) before making any changes.
- 2. Write the GPTM Configuration Register (GPTMCFG) with a value of 0x0000.0000.
- 3. Configure the TnMR field in the GPTM Timer n Mode Register (GPTMTnMR):
 - **a.** Write a value of 0x1 for One-Shot mode.
 - **b.** Write a value of 0x2 for Periodic mode.
- **4.** Optionally configure the TnSNAPS, TnWOT, TnMTE, and TnCDIR bits in the **GPTMTnMR** register to select whether to capture the value of the free-running timer at time-out, use an external trigger to start counting, configure an additional trigger or interrupt, and count up or down.
- 5. Load the start value into the GPTM Timer n Interval Load Register (GPTMTnILR).
- **6.** If interrupts are required, set the appropriate bits in the **GPTM Interrupt Mask Register (GPTMIMR)**.

- 7. Set the TnEN bit in the **GPTMCTL** register to enable the timer and start counting.
- 8. Poll the **GPTMRIS** register or wait for the interrupt to be generated (if enabled). In both cases, the status flags are cleared by writing a 1 to the appropriate bit of the **GPTM Interrupt Clear Register (GPTMICR)**.

If the TnMIE bit in the **GPTMTnMR** register is set, the RTCRIS bit in the **GPTMRIS** register is set, and the timer continues counting. In One-Shot mode, the timer stops counting after the time-out event. To re-enable the timer, repeat the sequence. A timer configured in Periodic mode reloads the timer and continues counting after the time-out event.

11.4.2 Real-Time Clock (RTC) Mode

To use the RTC mode, the timer must have a 32.768-KHz input signal on an even CCP input. To enable the RTC feature, follow these steps:

- 1. Ensure the timer is disabled (the TAEN bit is cleared) before making any changes.
- 2. Write the GPTM Configuration Register (GPTMCFG) with a value of 0x0000.0001.
- 3. Write the match value to the GPTM Timer n Match Register (GPTMTnMATCHR).
- 4. Set/clear the RTCEN bit in the GPTM Control Register (GPTMCTL) as needed.
- 5. If interrupts are required, set the RTCIM bit in the GPTM Interrupt Mask Register (GPTMIMR).
- 6. Set the TAEN bit in the **GPTMCTL** register to enable the timer and start counting.

When the timer count equals the value in the **GPTMTnMATCHR** register, the GPTM asserts the RTCRIS bit in the **GPTMRIS** register and continues counting until Timer A is disabled or a hardware reset. The interrupt is cleared by writing the RTCCINT bit in the **GPTMICR** register. Note that if the **GPTMTnILR** register is loaded with a new value, the timer begins counting at this new value and continues until it reaches 0xFFFF.FFFF, at which point it rolls over.

11.4.3 Input Edge-Count Mode

A timer is configured to Input Edge-Count mode by the following sequence:

- 1. Ensure the timer is disabled (the TnEN bit is cleared) before making any changes.
- 2. Write the **GPTM Configuration (GPTMCFG)** register with a value of 0x0000.0004.
- 3. In the **GPTM Timer Mode (GPTMTnMR)** register, write the TnCMR field to 0x0 and the TnMR field to 0x3.
- **4.** Configure the type of event(s) that the timer captures by writing the Tnevent field of the **GPTM Control (GPTMCTL)** register.
- 5. If a prescaler is to be used, write the prescale value to the GPTM Timer n Prescale Register (GPTMTnPR).
- 6. Load the timer start value into the GPTM Timer n Interval Load (GPTMTnILR) register.
- Load the prescaler match value (if any) in the GPTM Timer n Prescale Match (GPTMTnPMR) register.

- **8.** Load the event count into the **GPTM Timer n Match (GPTMTnMATCHR)** register. Note that when executing an up-count, the value of **GPTMTnPR** and **GPTMTnILR** must be greater than the value of **GPTMTnPMR** and **GPTMTnMATCHR**.
- 9. If interrupts are required, set the CnMIM bit in the GPTM Interrupt Mask (GPTMIMR) register.
- 10. Set the TnEN bit in the GPTMCTL register to enable the timer and begin waiting for edge events.
- 11. Poll the CnMRIS bit in the **GPTMRIS** register or wait for the interrupt to be generated (if enabled). In both cases, the status flags are cleared by writing a 1 to the CnMCINT bit of the **GPTM** Interrupt Clear (GPTMICR) register.

When counting down in Input Edge-Count Mode, the timer stops after the programmed number of edge events has been detected. To re-enable the timer, ensure that the TnEN bit is cleared and repeat #4 on page 723 through #9 on page 724.

11.4.4 Input Edge Timing Mode

A timer is configured to Input Edge Timing mode by the following sequence:

- **1.** Ensure the timer is disabled (the TnEN bit is cleared) before making any changes.
- 2. Write the **GPTM Configuration (GPTMCFG)** register with a value of 0x0000.0004.
- 3. In the **GPTM Timer Mode (GPTMTnMR)** register, write the TnCMR field to 0x1 and the TnMR field to 0x3.
- **4.** Configure the type of event that the timer captures by writing the TREVENT field of the **GPTM Control (GPTMCTL)** register.
- 5. If a prescaler is to be used, write the prescale value to the GPTM Timer n Prescale Register (GPTMTnPR).
- 6. Load the timer start value into the **GPTM Timer n Interval Load (GPTMTnILR)** register.
- 7. If interrupts are required, set the CnEIM bit in the GPTM Interrupt Mask (GPTMIMR) register.
- 8. Set the Then bit in the **GPTM Control (GPTMCTL)** register to enable the timer and start counting.
- 9. Poll the Cners bit in the GPTMRIS register or wait for the interrupt to be generated (if enabled). In both cases, the status flags are cleared by writing a 1 to the Cnecint bit of the GPTM Interrupt Clear (GPTMICR) register. The time at which the event happened can be obtained by reading the GPTM Timer n (GPTMTnR) register.

In Input Edge Timing mode, the timer continues running after an edge event has been detected, but the timer interval can be changed at any time by writing the **GPTMTnILR** register. The change takes effect at the next cycle after the write.

11.4.5 PWM Mode

A timer is configured to PWM mode using the following sequence:

- 1. Ensure the timer is disabled (the TnEN bit is cleared) before making any changes.
- 2. Write the **GPTM Configuration (GPTMCFG)** register with a value of 0x0000.0004.

- 3. In the **GPTM Timer Mode (GPTMTnMR)** register, set the TnAMS bit to 0x1, the TnCMR bit to 0x0, and the TnMR field to 0x2.
- **4.** Configure the output state of the PWM signal (whether or not it is inverted) in the TnPWML field of the **GPTM Control (GPTMCTL)** register.
- 5. If a prescaler is to be used, write the prescale value to the GPTM Timer n Prescale Register (GPTMTnPR).
- 6. If PWM interrupts are used, configure the interrupt condition in the Tnevent field in the GPTMCTL register and enable the interrupts by setting the TnPWMIE bit in the GPTMTnMR register. Note that edge detect interrupt behavior is reversed when the PWM output is inverted (see page 737).
- 7. Load the timer start value into the GPTM Timer n Interval Load (GPTMTnILR) register.
- 8. Load the GPTM Timer n Match (GPTMTnMATCHR) register with the match value.
- 9. Set the TnEN bit in the **GPTM Control (GPTMCTL)** register to enable the timer and begin generation of the output PWM signal.

In PWM Timing mode, the timer continues running after the PWM signal has been generated. The PWM period can be adjusted at any time by writing the **GPTMTnILR** register, and the change takes effect at the next cycle after the write.

11.5 Register Map

Table 11-12 on page 726 lists the GPTM registers. The offset listed is a hexadecimal increment to the register's address, relative to that timer's base address:

- 16/32-bit Timer 0: 0x4003.0000
- 16/32-bit Timer 1: 0x4003.1000
- 16/32-bit Timer 2: 0x4003,2000
- 16/32-bit Timer 3: 0x4003.3000
- 16/32-bit Timer 4: 0x4003.4000
- 16/32-bit Timer 5: 0x4003.5000
- 32/64-bit Wide Timer 0: 0x4003.6000
- 32/64-bit Wide Timer 1: 0x4003.7000
- 32/64-bit Wide Timer 2: 0x4004.C000
- 32/64-bit Wide Timer 3: 0x4004.D000
- 32/64-bit Wide Timer 4: 0x4004.E000
- 32/64-bit Wide Timer 5: 0x4004.F000

The SIZE field in the **GPTM Peripheral Properties (GPTMPP)** register identifies whether a module has a 16/32-bit or 32/64-bit wide timer.

Note that the GP Timer module clock must be enabled before the registers can be programmed (see page 328 or page 348). There must be a delay of 3 system clocks after the Timer module clock is enabled before any Timer module registers are accessed.

Table 11-12. Timers Register Map

Offset	Name	Туре	Reset	Description	See page
0x000	GPTMCFG	R/W	0x0000.0000	GPTM Configuration	727
0x004	GPTMTAMR	R/W	0x0000.0000	GPTM Timer A Mode	729
0x008	GPTMTBMR	R/W	0x0000.0000	GPTM Timer B Mode	733
0x00C	GPTMCTL	R/W	0x0000.0000	GPTM Control	737
0x010	GPTMSYNC	R/W	0x0000.0000	GPTM Synchronize	741
0x018	GPTMIMR	R/W	0x0000.0000	GPTM Interrupt Mask	745
0x01C	GPTMRIS	RO	0x0000.0000	GPTM Raw Interrupt Status	748
0x020	GPTMMIS	RO	0x0000.0000	GPTM Masked Interrupt Status	751
0x024	GPTMICR	W1C	0x0000.0000	GPTM Interrupt Clear	754
0x028	GPTMTAILR	R/W	0xFFFF.FFFF	GPTM Timer A Interval Load	756
0x02C	GPTMTBILR	R/W	-	GPTM Timer B Interval Load	757
0x030	GPTMTAMATCHR	R/W	0xFFFF.FFFF	GPTM Timer A Match	758
0x034	GPTMTBMATCHR	R/W	-	GPTM Timer B Match	759
0x038	GPTMTAPR	R/W	0x0000.0000	GPTM Timer A Prescale	760
0x03C	GPTMTBPR	R/W	0x0000.0000	GPTM Timer B Prescale	761
0x040	GPTMTAPMR	R/W	0x0000.0000	GPTM TimerA Prescale Match	762
0x044	GPTMTBPMR	R/W	0x0000.0000	GPTM TimerB Prescale Match	763
0x048	GPTMTAR	RO	0xFFFF.FFFF	GPTM Timer A	764
0x04C	GPTMTBR	RO	-	GPTM Timer B	765
0x050	GPTMTAV	RW	0xFFFF.FFFF	GPTM Timer A Value	766
0x054	GPTMTBV	RW	-	GPTM Timer B Value	767
0x058	GPTMRTCPD	RO	0x0000.7FFF	GPTM RTC Predivide	768
0x05C	GPTMTAPS	RO	0x0000.0000	GPTM Timer A Prescale Snapshot	769
0x060	GPTMTBPS	RO	0x0000.0000	GPTM Timer B Prescale Snapshot	770
0x064	GPTMTAPV	RO	0x0000.0000	GPTM Timer A Prescale Value	771
0x068	GPTMTBPV	RO	0x0000.0000	GPTM Timer B Prescale Value	772
0xFC0	GPTMPP	RO	0x0000.0000	GPTM Peripheral Properties	773

11.6 Register Descriptions

The remainder of this section lists and describes the GPTM registers, in numerical order by address offset.

Register 1: GPTM Configuration (GPTMCFG), offset 0x000

This register configures the global operation of the GPTM module. The value written to this register determines whether the GPTM is in 32- or 64-bit mode (concatenated timers) or in 16- or 32-bit mode (individual, split timers).

Important: Bits in this register should only be changed when the TAEN and TBEN bits in the **GPTMCTL** register are cleared.

GPTM Configuration (GPTMCFG) 16/32-bit Timer 0 base: 0x4003.0000 16/32-bit Timer 1 base: 0x4003.1000 16/32-bit Timer 2 base: 0x4003.2000 16/32-bit Timer 3 base: 0x4003.3000 16/32-bit Timer 4 base: 0x4003.4000 16/32-bit Timer 5 base: 0x4003.5000 32/64-bit Wide Timer 0 base: 0x4003.6000 32/64-bit Wide Timer 1 base: 0x4003.7000 32/64-bit Wide Timer 2 base: 0x4004.C000 32/64-bit Wide Timer 3 base: 0x4004.D000 32/64-bit Wide Timer 4 base: 0x4004.E000 32/64-bit Wide Timer 5 base: 0x4004.F000 Offset 0x000 Type R/W, reset 0x0000.0000 31 28 25 16 reserved RΩ RΩ RΩ RΩ RΩ RO RΩ RΩ Type RO RO RO RO RO RO RO RO Reset n 0 0 0 0 0 0 0 0 0 0 0 0 0 0 0 2 15 13 12 10 9 8 6 5 3 0 14 11 **GPTMCFG** RO R/W R/W R/W RO Type Reset 0 0 Bit/Field Name Type Reset Description 31:3 reserved RO 0x0000.000 Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be

preserved across a read-modify-write operation.

Bit/Field	Name	Туре	Reset	Description	
2:0	GPTMCFG	R/W	0x0	GPTM Configuration The GPTMCFG values are defined as follows:	
				Value Description	
				0x0 For a 16/32-bit timer, this value selects the 32-bit time configuration.	er
				For a 32/64-bit wide timer, this value selects the 64-bi configuration.	t timer
				Ox1 For a 16/32-bit timer, this value selects the 32-bit real-clock (RTC) counter configuration.	-time
				For a 32/64-bit wide timer, this value selects the 64-bi real-time clock (RTC) counter configuration.	it
				0x2-0x3 Reserved	
				Ox4 For a 16/32-bit timer, this value selects the 16-bit time configuration.	er
				For a 32/64-bit wide timer, this value selects the 32-bi configuration.	t timer
				The function is controlled by bits 1:0 of GPTMTAMR a GPTMTBMR .	and
				0x5-0x7 Reserved	

Register 2: GPTM Timer A Mode (GPTMTAMR), offset 0x004

This register configures the GPTM based on the configuration selected in the **GPTMCFG** register. When in PWM mode, set the TAAMS bit, clear the TACMR bit, and configure the TAMR field to 0x1 or 0x2.

This register controls the modes for Timer A when it is used individually. When Timer A and Timer B are concatenated, this register controls the modes for both Timer A and Timer B, and the contents of **GPTMTBMR** are ignored.


Important: Bits in this register should only be changed when the TAEN bit in the **GPTMCTL** register is cleared.

GPTM Timer A Mode (GPTMTAMR)

16/32-bit Timer 0 base: 0x4003.0000
16/32-bit Timer 1 base: 0x4003.1000
16/32-bit Timer 2 base: 0x4003.2000
16/32-bit Timer 3 base: 0x4003.3000
16/32-bit Timer 4 base: 0x4003.4000
16/32-bit Timer 5 base: 0x4003.5000
32/64-bit Wide Timer 0 base: 0x4003.6000
32/64-bit Wide Timer 1 base: 0x4003.7000
32/64-bit Wide Timer 2 base: 0x4004.C000
32/64-bit Wide Timer 3 base: 0x4004.D000
32/64-bit Wide Timer 4 base: 0x4004.E000
32/64-bit Wide Timer 5 base: 0x4004.F000

Offset 0x004

Type R/W, reset 0x0000.0000



Bit/Field	Name	Туре	Reset	Description
31:12	reserved	RO	0x0000.00	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
11	TAPLO	R/W	0	GPTM Timer A PWM Legacy Operation

Value Description

- 0 Legacy operation with CCP pin driven Low when the GPTMTAILR is reloaded after the timer reaches 0.
- 1 CCP is driven High when the GPTMTAILR is reloaded after the timer reaches 0.

This bit is only valid in PWM mode.

Bit/Field	Name	Туре	Reset	Description
10	TAMRSU	R/W	0	GPTM Timer A Match Register Update
				Value Description
				Update the GPTMTAMATCHR register and the GPTMTAPR register, if used, on the next cycle.
				1 Update the GPTMTAMATCHR register and the GPTMTAPR register, if used, on the next timeout.
				If the timer is disabled (TAEN is clear) when this bit is set, GPTMTAMATCHR and GPTMTAPR are updated when the timer is enabled. If the timer is stalled (TASTALL is set), GPTMTAMATCHR and GPTMTAPR are updated according to the configuration of this bit.
9	TAPWMIE	R/W	0	GPTM Timer A PWM Interrupt Enable
				This bit enables interrupts in PWM mode on rising, falling, or both edges of the CCP output, as defined by the TAEVENT field in the $\mbox{\bf GPTMCTL}$ register.
				Value Description
				O Capture event interrupt is disabled.
				1 Capture event interrupt is enabled.
				This bit is only valid in PWM mode.
8	TAILD	R/W	0	GPTM Timer A Interval Load Write
				Value Description
				Update the GPTMTAR and GPTMTAV registers with the value in the GPTMTAILR register on the next cycle. Also update the GPTMTAPS and GPTMTAPV registers with the value in the GPTMTAPR register on the next cycle.
				Update the GPTMTAR and GPTMTAV registers with the value in the GPTMTAILR and GPTMTAPV registers on the next timeout. Also update the GPTMTAPS register with the value in the GPTMTAPR register on the next timeout.
				Note the state of this bit has no effect when counting up.
				The bit descriptions above apply if the timer is enabled and running. If the timer is disabled (TAEN is clear) when this bit is set, GPTMTAR, GPTMTAV, GPTMTAPS, and GPTMTAPV are updated when the timer is enabled. If the timer is stalled (TASTALL is set), GPTMTAR and GPTMTAPS are updated according to the configuration of this bit.
7	TASNAPS	R/W	0	GPTM Timer A Snap-Shot Mode
				Value Description
				0 Snap-shot mode is disabled.
				If Timer A is configured in the periodic mode, the actual free-running value of Timer A is loaded at the time-out event into the GPTM Timer A (GPTMTAR) register. If the timer prescaler is used, the prescaler snapshot is loaded into the GPTM Timer A (GPTMTAPR) .

Bit/Field	Name	Туре	Reset	Description
6	TAWOT	R/W	0	GPTM Timer A Wait-on-Trigger
				Value Description
				O Timer A begins counting as soon as it is enabled.
				If Timer A is enabled (TAEN is set in the GPTMCTL register), Timer A does not begin counting until it receives a trigger from the timer in the previous position in the daisy chain, see Figure 11-9 on page 719. This function is valid for one-shot, periodic, and PWM modes.
				This bit must be clear for GP Timer Module 0, Timer A.
5	TAMIE	R/W	0	GPTM Timer A Match Interrupt Enable
				Value Description
				The match interrupt is disabled for match events. Additionally, triggers to the DMA and ADC on match events are prevented.
				An interrupt is generated when the match value in the GPTMTAMATCHR register is reached in the one-shot and periodic modes.
4	TACDIR	R/W	0	GPTM Timer A Count Direction
				Value Description
				0 The timer counts down.
				1 The timer counts up. When counting up, the timer starts from a value of 0x0.
				When in PWM or RTC mode, the status of this bit is ignored. PWM mode always counts down and RTC mode always counts up.
3	TAAMS	R/W	0	GPTM Timer A Alternate Mode Select
				The TAAMS values are defined as follows:
				Value Description
				0 Capture or compare mode is enabled.
				1 PWM mode is enabled.
				Note: To enable PWM mode, you must also clear the TACMR bit and configure the TAMR field to 0x1 or 0x2.
2	TACMR	R/W	0	GPTM Timer A Capture Mode
				The TACMR values are defined as follows:
				Value Description
				0 Edge-Count mode
				1 Edge-Time mode

Bit/Field	Name	Type	Reset	Description
1:0	TAMR	R/W	0x0	GPTM Timer A Mode The TAMR values are defined as follows:
				Value Description
				0x0 Reserved
				0x1 One-Shot Timer mode
				0x2 Periodic Timer mode
				0x3 Capture mode
				The Timer mode is based on the timer configuration defined by bits 2:0 in the GPTMCFG register.

Register 3: GPTM Timer B Mode (GPTMTBMR), offset 0x008

This register configures the GPTM based on the configuration selected in the **GPTMCFG** register. When in PWM mode, set the TBAMS bit, clear the TBCMR bit, and configure the TBMR field to 0x1 or 0x2.


This register controls the modes for Timer B when it is used individually. When Timer A and Timer B are concatenated, this register is ignored and **GPTMTAMR** controls the modes for both Timer A and Timer B.

Important: Bits in this register should only be changed when the TBEN bit in the **GPTMCTL** register is cleared.

GPTM Timer B Mode (GPTMTBMR)

16/32-bit Timer 0 base: 0x4003.0000
16/32-bit Timer 1 base: 0x4003.1000
16/32-bit Timer 2 base: 0x4003.2000
16/32-bit Timer 3 base: 0x4003.3000
16/32-bit Timer 4 base: 0x4003.4000
16/32-bit Timer 5 base: 0x4003.5000
32/64-bit Wide Timer 0 base: 0x4003.6000
32/64-bit Wide Timer 1 base: 0x4003.7000
32/64-bit Wide Timer 2 base: 0x4004.C000
32/64-bit Wide Timer 3 base: 0x4004.D000
32/64-bit Wide Timer 4 base: 0x4004.E000
32/64-bit Wide Timer 5 base: 0x4004.F000

Offset 0x008 Type R/W, reset 0x0000.0000



Bit/Field	Name	Type	Reset	Description
31:12	reserved	RO	0x0000.00	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
11	TBPLO	R/W	0	GPTM Timer B PWM Legacy Operation

Value Description

- 0 Legacy operation with CCP pin driven Low when the GPTMTAILR is reloaded after the timer reaches 0.
- 1 CCP is driven High when the GPTMTAILR is reloaded after the timer reaches 0.

This bit is only valid in PWM mode.

Bit/Field	Name	Туре	Reset	Description
10	TBMRSU	R/W	0	GPTM Timer B Match Register Update
				Value Description
				Update the GPTMTBMATCHR register and the GPTMTBPR register, if used, on the next cycle.
				1 Update the GPTMTBMATCHR register and the GPTMTBPR register, if used, on the next timeout.
				If the timer is disabled (TBEN is clear) when this bit is set, GPTMTBMATCHR and GPTMTBPR are updated when the timer is enabled. If the timer is stalled (TBSTALL is set), GPTMTBMATCHR and GPTMTBPR are updated according to the configuration of this bit.
9	TBPWMIE	R/W	0	GPTM Timer B PWM Interrupt Enable
				This bit enables interrupts in PWM mode on rising, falling, or both edges of the CCP output as defined by the ${\tt TBEVENT}$ field in the ${\tt GPTMCTL}$ register.
				Value Description
				0 Capture event interrupt is disabled.
				1 Capture event is enabled.
				This bit is only valid in PWM mode.
8	TBILD	R/W	0	GPTM Timer B Interval Load Write
				Value Description
				Update the GPTMTBR and GPTMTBV registers with the value in the GPTMTBILR register on the next cycle. Also update the GPTMTBPS and GPTMTBPV registers with the value in the GPTMTBPR register on the next cycle.
				Update the GPTMTBR and GPTMTBV registers with the value in the GPTMTBILR register on the next timeout. Also update the GPTMTBPS and GPTMTBPV registers with the value in the GPTMTBPR register on the next timeout.
				Note the state of this bit has no effect when counting up.
				The bit descriptions above apply if the timer is enabled and running. If the timer is disabled (TBEN is clear) when this bit is set, GPTMTBR, GPTMTBV, GPTMTBPS, and GPTMTBPV are updated when the timer is enabled. If the timer is stalled (TBSTALL is set), GPTMTBR and GPTMTBPS are updated according to the configuration of this bit.
7	TBSNAPS	R/W	0	GPTM Timer B Snap-Shot Mode
				Value Description
				0 Snap-shot mode is disabled.
				If Timer B is configured in the periodic mode, the actual free-running value of Timer B is loaded at the time-out event into the GPTM Timer B (GPTMTBR) register. If the timer prescaler is used, the prescaler snapshot is loaded into the GPTM Timer B (GPTMTBPR) .

Bit/Field	Name	Туре	Reset	Description
6	TBWOT	R/W	0	GPTM Timer B Wait-on-Trigger
				Value Description
				O Timer B begins counting as soon as it is enabled.
				If Timer B is enabled (TBEN is set in the GPTMCTL register), Timer B does not begin counting until it receives an it receives a trigger from the timer in the previous position in the daisy chain, see Figure 11-9 on page 719. This function is valid for one-shot, periodic, and PWM modes.
5	ТВМІЕ	R/W	0	GPTM Timer B Match Interrupt Enable
				Value Description
				The match interrupt is disabled for match events. Additionally, triggers to the DMA and ADC on match events are prevented.
				An interrupt is generated when the match value in the GPTMTBMATCHR register is reached in the one-shot and periodic modes.
4	TBCDIR	R/W	0	GPTM Timer B Count Direction
				Value Description
				0 The timer counts down.
				1 The timer counts up. When counting up, the timer starts from a value of 0x0.
				When in PWM or RTC mode, the status of this bit is ignored. PWM mode always counts down and RTC mode always counts up.
3	TBAMS	R/W	0	GPTM Timer B Alternate Mode Select
				The TBAMS values are defined as follows:
				Value Description
				0 Capture or compare mode is enabled.
				1 PWM mode is enabled.
				Note: To enable PWM mode, you must also clear the TBCMR bit and configure the TBMR field to 0x1 or 0x2.
2	TBCMR	R/W	0	GPTM Timer B Capture Mode
				The TBCMR values are defined as follows:
				Value Description
				0 Edge-Count mode
				1 Edge-Time mode
				•

Bit/Field	Name	Туре	Reset	Description
1:0	TBMR	R/W	0x0	GPTM Timer B Mode
				The TBMR values are defined as follows:
				Value Description
				0x0 Reserved
				0x1 One-Shot Timer mode
				0x2 Periodic Timer mode
				0x3 Capture mode
				The timer mode is based on the timer configuration defined by bits 2:0 in the GPTMCFG register.

Register 4: GPTM Control (GPTMCTL), offset 0x00C

This register is used alongside the **GPTMCFG** and **GMTMTnMR** registers to fine-tune the timer configuration, and to enable other features such as timer stall and the output trigger. The output trigger can be used to initiate transfers on the ADC module.


Important: Bits in this register should only be changed when the TnEN bit for the respective timer is cleared.

GPTM Control (GPTMCTL)

16/32-bit Timer 0 base: 0x4003.0000
16/32-bit Timer 1 base: 0x4003.1000
16/32-bit Timer 2 base: 0x4003.2000
16/32-bit Timer 3 base: 0x4003.3000
16/32-bit Timer 4 base: 0x4003.4000
16/32-bit Timer 5 base: 0x4003.5000
32/64-bit Wide Timer 0 base: 0x4003.6000
32/64-bit Wide Timer 1 base: 0x4004.C000
32/64-bit Wide Timer 2 base: 0x4004.D000
32/64-bit Wide Timer 3 base: 0x4004.E000
32/64-bit Wide Timer 4 base: 0x4004.E000
32/64-bit Wide Timer 5 base: 0x4004.E000

Offset 0x00C

Type R/W, reset 0x0000.0000



Bit/Field	Name	Туре	Reset	Description
31:15	reserved	RO	0x0000	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
14	TBPWML	R/W	0	GPTM Timer B PWM Output Level The TBPWML values are defined as follows: Value Description 0 Output is unaffected. 1 Output is inverted.
13	ТВОТЕ	R/W	0	GPTM Timer B Output Trigger Enable The TBOTE values are defined as follows:

Value Description

- 0 The output Timer B ADC trigger is disabled.
- 1 The output Timer B ADC trigger is enabled.

In addition, the ADC must be enabled and the timer selected as a trigger source with the ${\tt EMn}$ bit in the **ADCEMUX** register (see page 833).

Bit/Field	Name	Туре	Reset	Description
12	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
11:10	TBEVENT	R/W	0x0	GPTM Timer B Event Mode The TBEVENT values are defined as follows:
				Value Description
				0x0 Positive edge
				0x1 Negative edge
				0x2 Reserved
				0x3 Both edges
				Note: If PWM output inversion is enabled, edge detection interrupt behavior is reversed. Thus, if a positive-edge interrupt trigger has been set and the PWM inversion generates a postive edge, no event-trigger interrupt asserts. Instead, the interrupt is generated on the negative edge of the PWM signal.
9	TBSTALL	R/W	0	GPTM Timer B Stall Enable
				The TBSTALL values are defined as follows:
				Value Description
				Timer B continues counting while the processor is halted by the debugger.
				1 Timer B freezes counting while the processor is halted by the debugger.
				If the processor is executing normally, the ${\tt TBSTALL}$ bit is ignored.
8	TBEN	R/W	0	GPTM Timer B Enable
				The TBEN values are defined as follows:
				Value Description
				0 Timer B is disabled.
				Timer B is enabled and begins counting or the capture logic is enabled based on the GPTMCFG register.
7	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
6	TAPWML	R/W	0	GPTM Timer A PWM Output Level
				The TAPWML values are defined as follows:
				Value Description
				0 Output is unaffected.
				1 Output is inverted.

Bit/Field	Name	Туре	Reset	Description
5	TAOTE	R/W	0	GPTM Timer A Output Trigger Enable The TAOTE values are defined as follows:
				Value Description
				0 The output Timer A ADC trigger is disabled.
				1 The output Timer A ADC trigger is enabled.
				In addition, the ADC must be enabled and the timer selected as a trigger source with the ${\tt EMn}$ bit in the ADCEMUX register (see page 833).
4	RTCEN	R/W	0	GPTM RTC Stall Enable
				The RTCEN values are defined as follows:
				Value Description
				0 RTC counting freezes while the processor is halted by the debugger.
				1 RTC counting continues while the processor is halted by the debugger.
				If the RTCEN bit is set, it prevents the timer from stalling in all operating modes, even if ${\tt TnSTALL}$ is set.
3:2	TAEVENT	R/W	0x0	GPTM Timer A Event Mode
				The TAEVENT values are defined as follows:
				Value Description
				0x0 Positive edge
				0x1 Negative edge
				0x2 Reserved
				0x3 Both edges
				Note: If PWM output inversion is enabled, edge detection interrupt behavior is reversed. Thus, if a positive-edge interrupt trigger has been set and the PWM inversion generates a postive edge, no event-trigger interrupt asserts. Instead, the interrupt is generated on the negative edge of the PWM signal.
1	TASTALL	R/W	0	GPTM Timer A Stall Enable
				The TASTALL values are defined as follows:
				Value Description
				Timer A continues counting while the processor is halted by the debugger.
				1 Timer A freezes counting while the processor is halted by the debugger.

If the processor is executing normally, the ${\tt TASTALL}$ bit is ignored.

Bit/Field	Name	Туре	Reset	Description
0	TAEN	R/W	0	GPTM Timer A Enable The TAEN values are defined as follows: Value Description 0 Timer A is disabled. 1 Timer A is enabled and begins counting or the capture logic is enabled based on the GPTMCFG register.

Register 5: GPTM Synchronize (GPTMSYNC), offset 0x010

Note: This register is only implemented on GPTM Module 0 only.


This register allows software to synchronize a number of timers.

GPTM Synchronize (GPTMSYNC)

16/32-bit Timer 0 base: 0x4003.0000
16/32-bit Timer 1 base: 0x4003.1000
16/32-bit Timer 2 base: 0x4003.2000
16/32-bit Timer 3 base: 0x4003.3000
16/32-bit Timer 4 base: 0x4003.4000
16/32-bit Timer 5 base: 0x4003.5000
32/64-bit Wide Timer 0 base: 0x4003.6000
32/64-bit Wide Timer 1 base: 0x4003.7000
32/64-bit Wide Timer 2 base: 0x4004.C000
32/64-bit Wide Timer 3 base: 0x4004.D000
32/64-bit Wide Timer 4 base: 0x4004.E000
32/64-bit Wide Timer 5 base: 0x4004.E000

Offset 0x010

Type R/W, reset 0x0000.0000



Bit/Field	Name	Type	Reset	Description
31:24	reserved	RO	0x00	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
23:22	SYNCWT5	R/W	0x0	Synchronize GPTM 32/64-Bit Timer 5

The SYNCWT5 values are defined as follows:

Value Description

0x0 GPTM 32/64-Bit Timer 5 is not affected.

0x1 A timeout event for Timer A of GPTM 32/64-Bit Timer 5 is

triggered.

0x2 A timeout event for Timer B of GPTM 32/64-Bit Timer 5 is triggered.

0x3 A timeout event for both Timer A and Timer B of GPTM 32/64-Bit Timer 5 is triggered.

Bit/Field	Name	Туре	Reset	Description
21:20	SYNCWT4	R/W	0x0	Synchronize GPTM 32/64-Bit Timer 4
				The SYNCWT4 values are defined as follows:
				Value Description
				0x0 GPTM 32/64-Bit Timer 4 is not affected.
				0x1 A timeout event for Timer A of GPTM 32/64-Bit Timer 4 is triggered.
				0x2 A timeout event for Timer B of GPTM 32/64-Bit Timer 4 is triggered.
				0x3 A timeout event for both Timer A and Timer B of GPTM 32/64-Bit Timer 4 is triggered.
19:18	SYNCWT3	R/W	0x0	Synchronize GPTM 32/64-Bit Timer 3
				The SYNCWT3 values are defined as follows:
				Value Description
				0x0 GPTM 32/64-Bit Timer 3 is not affected.
				0x1 A timeout event for Timer A of GPTM 32/64-Bit Timer 3 is triggered.
				0x2 A timeout event for Timer B of GPTM 32/64-Bit Timer 3 is triggered.
				0x3 A timeout event for both Timer A and Timer B of GPTM 32/64-Bit Timer 3 is triggered.
17:16	SYNCWT2	R/W	0x0	Synchronize GPTM 32/64-Bit Timer 2
				The SYNCWT2 values are defined as follows:
				Value Description
				0x0 GPTM 32/64-Bit Timer 2 is not affected.
				0x1 A timeout event for Timer A of GPTM 32/64-Bit Timer 2 is triggered.
				0x2 A timeout event for Timer B of GPTM 32/64-Bit Timer 2 is triggered.
				0x3 A timeout event for both Timer A and Timer B of GPTM 32/64-Bit Timer 2 is triggered.
15:14	SYNCWT1	R/W	0x0	Synchronize GPTM 32/64-Bit Timer 1
				The SYNCWT1 values are defined as follows:
				Value Description
				0x0 GPTM 32/64-Bit Timer 1 is not affected.
				0x1 A timeout event for Timer A of GPTM 32/64-Bit Timer 1 is triggered.
				0x2 A timeout event for Timer B of GPTM 32/64-Bit Timer 1 is triggered.
				0x3 A timeout event for both Timer A and Timer B of GPTM 32/64-Bit Timer 1 is triggered.

Bit/Field	Name	Туре	Reset	Description
13:12	SYNCWT0	R/W	0x0	Synchronize GPTM 32/64-Bit Timer 0
				The SYNCWT0 values are defined as follows:
				Value Description
				0x0 GPTM 32/64-Bit Timer 0 is not affected.
				0x1 A timeout event for Timer A of GPTM 32/64-Bit Timer 0 is triggered.
				0x2 A timeout event for Timer B of GPTM 32/64-Bit Timer 0 is triggered.
				0x3 A timeout event for both Timer A and Timer B of GPTM 32/64-Bit Timer 0 is triggered.
11:10	SYNCT5	R/W	0x0	Synchronize GPTM 16/32-Bit Timer 5
				The SYNCT5 values are defined as follows:
				Value Description
				0x0 GPTM 16/32-Bit Timer 5 is not affected.
				0x1 A timeout event for Timer A of GPTM 16/32-Bit Timer 5 is triggered.
				0x2 A timeout event for Timer B of GPTM 16/32-Bit Timer 5 is triggered.
				0x3 A timeout event for both Timer A and Timer B of GPTM 16/32-Bit Timer 5 is triggered.
9:8	SYNCT4	R/W	0x0	Synchronize GPTM 16/32-Bit Timer 4
				The SYNCT4 values are defined as follows:
				Value Description
				0x0 GPTM 16/32-Bit Timer 4 is not affected.
				0x1 A timeout event for Timer A of GPTM 16/32-Bit Timer 4 is triggered.
				0x2 A timeout event for Timer B of GPTM 16/32-Bit Timer 4 is triggered.
				0x3 A timeout event for both Timer A and Timer B of GPTM 16/32-Bit Timer 4 is triggered.
7:6	SYNCT3	R/W	0x0	Synchronize GPTM 16/32-Bit Timer 3
				The SYNCT3 values are defined as follows:
				Value Description
				0x0 GPTM 16/32-Bit Timer 3 is not affected.
				0x1 A timeout event for Timer A of GPTM 16/32-Bit Timer 3 is triggered.
				0x2 A timeout event for Timer B of GPTM 16/32-Bit Timer 3 is triggered.
				0x3 A timeout event for both Timer A and Timer B of GPTM 16/32-Bit Timer 3 is triggered.

Bit/Field	Name	Туре	Reset	Description
5:4	SYNCT2	R/W	0x0	Synchronize GPTM 16/32-Bit Timer 2
				The SYNCT2 values are defined as follows:
				Value Description
				0x0 GPTM 16/32-Bit Timer 2 is not affected.
				0x1 A timeout event for Timer A of GPTM 16/32-Bit Timer 2 is triggered.
				0x2 A timeout event for Timer B of GPTM 16/32-Bit Timer 2 is triggered.
				0x3 A timeout event for both Timer A and Timer B of GPTM 16/32-Bit Timer 2 is triggered.
3:2	SYNCT1	R/W	0x0	Synchronize GPTM 16/32-Bit Timer 1
				The SYNCT1 values are defined as follows:
				Value Description
				0x0 GPTM 16/32-Bit Timer 1 is not affected.
				0x1 A timeout event for Timer A of GPTM 16/32-Bit Timer 1 is triggered.
				0x2 A timeout event for Timer B of GPTM 16/32-Bit Timer 1 is triggered.
				0x3 A timeout event for both Timer A and Timer B of GPTM 16/32-Bit Timer 1 is triggered.
1:0	SYNCT0	R/W	0x0	Synchronize GPTM 16/32-Bit Timer 0
				The SYNCTO values are defined as follows:
				Value Description
				0x0 GPTM 16/32-Bit Timer 0 is not affected.
				0x1 A timeout event for Timer A of GPTM 16/32-Bit Timer 0 is triggered.
				0x2 A timeout event for Timer B of GPTM 16/32-Bit Timer 0 is triggered.
				0x3 A timeout event for both Timer A and Timer B of GPTM 16/32-Bit Timer 0 is triggered.


Register 6: GPTM Interrupt Mask (GPTMIMR), offset 0x018

This register allows software to enable/disable GPTM controller-level interrupts. Setting a bit enables the corresponding interrupt, while clearing a bit disables it.

GPTM Interrupt Mask (GPTMIMR)

16/32-bit Timer 0 base: 0x4003.0000 16/32-bit Timer 1 base: 0x4003.1000 16/32-bit Timer 2 base: 0x4003.2000 16/32-bit Timer 3 base: 0x4003.3000 16/32-bit Timer 4 base: 0x4003.4000 16/32-bit Timer 5 base: 0x4003.5000 32/64-bit Wide Timer 0 base: 0x4003.6000 32/64-bit Wide Timer 1 base: 0x4003.7000 32/64-bit Wide Timer 2 base: 0x4004.C000 32/64-bit Wide Timer 3 base: 0x4004.D000 32/64-bit Wide Timer 4 base: 0x4004.E000 32/64-bit Wide Timer 5 base: 0x4004.F000

Offset 0x018
Type R/W, reset 0x0000.0000



Bit/Field	Name	Type	Reset	Description
31:17	reserved	RO	0x0000	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
16	WUEIM	R/W	0	32/64-Bit Wide GPTM Write Update Error Interrupt Mask
				The WUEIM values are defined as follows:
				Value Description
				0 Interrupt is disabled.
				1 Interrupt is enabled.
15:12	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
11	ТВМІМ	R/W	0	GPTM Timer B Match Interrupt Mask
				The TBMIM values are defined as follows:
				Value Description

0 Interrupt is disabled.

1 Interrupt is enabled.

Bit/Field	Name	Туре	Reset	Description
10	CBEIM	R/W	0	GPTM Timer B Capture Mode Event Interrupt Mask The CBEIM values are defined as follows:
				Value Description
				0 Interrupt is disabled.
				1 Interrupt is enabled.
9	СВМІМ	R/W	0	GPTM Timer B Capture Mode Match Interrupt Mask
				The CBMIM values are defined as follows:
				Value Description
				0 Interrupt is disabled.
				1 Interrupt is enabled.
8	TBTOIM	R/W	0	GPTM Timer B Time-Out Interrupt Mask
				The TBTOIM values are defined as follows:
				Value Description
				0 Interrupt is disabled.
				1 Interrupt is enabled.
7:5	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
4	TAMIM	R/W	0	GPTM Timer A Match Interrupt Mask
				The TAMIM values are defined as follows:
				Value Description
				0 Interrupt is disabled.
				1 Interrupt is enabled.
3	RTCIM	R/W	0	GPTM RTC Interrupt Mask
				The RTCIM values are defined as follows:
				Value Description
				0 Interrupt is disabled.
				1 Interrupt is enabled.
2	CAEIM	R/W	0	GPTM Timer A Capture Mode Event Interrupt Mask
				The CAEIM values are defined as follows:
				Value Description
				0 Interrupt is disabled.
				1 Interrupt is enabled.

Bit/Field	Name	Туре	Reset	Description
1	CAMIM	R/W	0	GPTM Timer A Capture Mode Match Interrupt Mask The CAMIM values are defined as follows:
				Value Description
				0 Interrupt is disabled.
				1 Interrupt is enabled.
0	TATOIM	R/W	0	GPTM Timer A Time-Out Interrupt Mask The TATOIM values are defined as follows:
				Value Description
				0 Interrupt is disabled.
				1 Interrupt is enabled.

Register 7: GPTM Raw Interrupt Status (GPTMRIS), offset 0x01C

This register shows the state of the GPTM's internal interrupt signal. These bits are set whether or not the interrupt is masked in the **GPTMIMR** register. Each bit can be cleared by writing a 1 to its corresponding bit in **GPTMICR**.

GPTM Raw Interrupt Status (GPTMRIS)

16/32-bit Timer 0 base: 0x4003.0000
16/32-bit Timer 1 base: 0x4003.1000
16/32-bit Timer 2 base: 0x4003.2000
16/32-bit Timer 3 base: 0x4003.3000
16/32-bit Timer 4 base: 0x4003.4000
16/32-bit Timer 5 base: 0x4003.5000
32/64-bit Wide Timer 0 base: 0x4003.6000
32/64-bit Wide Timer 1 base: 0x4004.000
32/64-bit Wide Timer 2 base: 0x4004.0000
32/64-bit Wide Timer 3 base: 0x4004.0000
32/64-bit Wide Timer 4 base: 0x4004.0000
32/64-bit Wide Timer 5 base: 0x4004.0000

TBMRIS


RO

0

Offset 0x01C

11

Type RO, reset 0x0000.0000



Bit/Field	Name	Туре	Reset	Description
31:17	reserved	RO	0x0000	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
16	WUERIS	R/W	0	32/64-Bit Wide GPTM Write Update Error Raw Interrupt Status
				Value Description
				0 No error.
				Either a Timer A register or a Timer B register was written twice in a row or a Timer A register was written before the corresponding Timer B register was written.
15:12	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be

Value Description

0 The match value has not been reached.

preserved across a read-modify-write operation.

GPTM Timer B Match Raw Interrupt

1 The TBMIE bit is set in the GPTMTBMR register, and the match values in the GPTMTBMATCHR and (optionally) GPTMTBPMR registers have been reached when configured in one-shot or periodic mode.

This bit is cleared by writing a 1 to the ${\tt TBMCINT}$ bit in the ${\bf GPTMICR}$ register.

Bit/Field	Name	Туре	Reset	Description
10	CBERIS	RO	0	GPTM Timer B Capture Mode Event Raw Interrupt
				Value Description
				0 The capture mode event for Timer B has not occurred.
				A capture mode event has occurred for Timer B. This interrupt asserts when the subtimer is configured in Input Edge-Time mode or when configured in PWM mode with the PWM interrupt enabled by setting the TBPWMIE bit in the GPTMTBMR .
				This bit is cleared by writing a 1 to the CBECINT bit in the GPTMICR register.
9	CBMRIS	RO	0	GPTM Timer B Capture Mode Match Raw Interrupt
				Value Description
				0 The capture mode match for Timer B has not occurred.
				The capture mode match has occurred for Timer B. This interrupt asserts when the values in the GPTMTBR and GPTMTBPR match the values in the GPTMTBMATCHR and GPTMTBPMR when configured in Input Edge-Time mode.
				This bit is cleared by writing a 1 to the CBMCINT bit in the GPTMICR register.
8	TBTORIS	RO	0	GPTM Timer B Time-Out Raw Interrupt
				Value Description
				0 Timer B has not timed out.
				Timer B has timed out. This interrupt is asserted when a one-shot or periodic mode timer reaches it's count limit (0 or the value loaded into GPTMTBILR, depending on the count direction).
				This bit is cleared by writing a 1 to the TBTOCINT bit in the GPTMICR register.
7:5	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
4	TAMRIS	RO	0	GPTM Timer A Match Raw Interrupt
				Value Description
				0 The match value has not been reached.
				The TAMIE bit is set in the GPTMTAMR register, and the match value in the GPTMTAMATCHR and (optionally) GPTMTAPMR registers have been reached when configured in one-shot or periodic mode.
				This bit is cleared by writing a 1 to the TAMCINT bit in the GPTMICR register.

Bit/Field	Name	Туре	Reset	Description
3	RTCRIS	RO	0	GPTM RTC Raw Interrupt
				Value Description O The RTC event has not occurred. 1 The RTC event has occurred. This bit is cleared by writing a 1 to the RTCCINT bit in the GPTMICR register.
2	CAERIS	RO	0	GPTM Timer A Capture Mode Event Raw Interrupt
				Value Description O The capture mode event for Timer A has not occurred. A capture mode event has occurred for Timer A. This interrupt asserts when the subtimer is configured in Input Edge-Time mode or when configured in PWM mode with the PWM interrupt enabled by setting the TAPWMIE bit in the GPTMTAMR. This bit is cleared by writing a 1 to the CAECINT bit in the GPTMICR register.
1	CAMRIS	RO	0	 GPTM Timer A Capture Mode Match Raw Interrupt Value Description The capture mode match for Timer A has not occurred. A capture mode match has occurred for Timer A. This interrupt asserts when the values in the GPTMTAR and GPTMTAPR match the values in the GPTMTAMATCHR and GPTMTAPMR when configured in Input Edge-Time mode. This bit is cleared by writing a 1 to the CAMCINT bit in the GPTMICR register.
0	TATORIS	RO	0	GPTM Timer A Time-Out Raw Interrupt Value Description 0 Timer A has not timed out. 1 Timer A has timed out. This interrupt is asserted when a one-shot or periodic mode timer reaches it's count limit (0 or the value loaded into GPTMTAILR, depending on the count direction). This bit is cleared by writing a 1 to the TATOCINT bit in the GPTMICR

This bit is cleared by writing a 1 to the TATOCINT bit in the **GPTMICR** register.

Register 8: GPTM Masked Interrupt Status (GPTMMIS), offset 0x020


This register show the state of the GPTM's controller-level interrupt. If an interrupt is unmasked in GPTMIMR, and there is an event that causes the interrupt to be asserted, the corresponding bit is set in this register. All bits are cleared by writing a 1 to the corresponding bit in GPTMICR.

GPTM Masked Interrupt Status (GPTMMIS)

16/32-bit Timer 0 base: 0x4003.0000 16/32-bit Timer 1 base: 0x4003.1000 16/32-bit Timer 2 base: 0x4003.2000 16/32-bit Timer 3 base: 0x4003.3000 16/32-bit Timer 4 base: 0x4003.4000 16/32-bit Timer 5 base: 0x4003.5000 32/64-bit Wide Timer 0 base: 0x4003.6000 32/64-bit Wide Timer 1 base: 0x4003.7000 32/64-bit Wide Timer 2 base: 0x4004.C000 32/64-bit Wide Timer 3 base: 0x4004.D000 32/64-bit Wide Timer 4 base: 0x4004.E000 32/64-bit Wide Timer 5 base: 0x4004.F000

Offset 0x020

Type RO, reset 0x0000.0000



Bit/Field	Name	Туре	Reset	Description
31:17	reserved	RO	0x0000	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
16	WUEMIS	RO	0	32/64-Bit Wide GPTM Write Update Error Masked Interrupt Status
				Value Description O An unmasked Write Update Error has not occurred. An unmasked Write Update Error has occurred.
15:12	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
11	TBMMIS	RO	0	GPTM Timer B Match Masked Interrupt

Value Description

- A Timer B Mode Match interrupt has not occurred or is masked.
- 1 An unmasked Timer B Mode Match interrupt has occurred.

This bit is cleared by writing a 1 to the TBMCINT bit in the GPTMICR register.

Bit/Field	Name	Туре	Reset	Description
10	CBEMIS	RO	0	GPTM Timer B Capture Mode Event Masked Interrupt
				Value Description
				O A Capture B event interrupt has not occurred or is masked.
				 An unmasked Capture B event interrupt has occurred.
				This bit is cleared by writing a 1 to the CBECINT bit in the GPTMICR register.
9	CBMMIS	RO	0	GPTM Timer B Capture Mode Match Masked Interrupt
				Value Description
				O A Capture B Mode Match interrupt has not occurred or is masked.
				 An unmasked Capture B Match interrupt has occurred.
				This bit is cleared by writing a 1 to the CBMCINT bit in the GPTMICR register.
8	TBTOMIS	RO	0	GPTM Timer B Time-Out Masked Interrupt
				Value Description
				0 A Timer B Time-Out interrupt has not occurred or is masked.
				 An unmasked Timer B Time-Out interrupt has occurred.
				This bit is cleared by writing a 1 to the ${\tt TBTOCINT}$ bit in the ${\bf GPTMICR}$ register.
7:5	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
4	TAMMIS	RO	0	GPTM Timer A Match Masked Interrupt
				Value Description
				0 A Timer A Mode Match interrupt has not occurred or is masked.
				 An unmasked Timer A Mode Match interrupt has occurred.
				This bit is cleared by writing a 1 to the ${\tt TAMCINT}$ bit in the ${\bf GPTMICR}$ register.
3	RTCMIS	RO	0	GPTM RTC Masked Interrupt
				Value Description
				O An RTC event interrupt has not occurred or is masked.
				 An unmasked RTC event interrupt has occurred.
				This bit is cleared by writing a 1 to the RTCCINT bit in the GPTMICR register.

Bit/Field	Name	Туре	Reset	Description
2	CAEMIS	RO	0	GPTM Timer A Capture Mode Event Masked Interrupt
				 Value Description A Capture A event interrupt has not occurred or is masked. An unmasked Capture A event interrupt has occurred. This bit is cleared by writing a 1 to the CAECINT bit in the GPTMICR
1	CAMMIS	RO	0	register. GPTM Timer A Capture Mode Match Masked Interrupt
				Value Description
				O A Capture A Mode Match interrupt has not occurred or is masked.
				 An unmasked Capture A Match interrupt has occurred.
				This bit is cleared by writing a 1 to the ${\tt CAMCINT}$ bit in the $\mbox{\bf GPTMICR}$ register.
0	TATOMIS	RO	0	GPTM Timer A Time-Out Masked Interrupt
				Value Description
				0 A Timer A Time-Out interrupt has not occurred or is masked.
				 An unmasked Timer A Time-Out interrupt has occurred.
				This bit is cleared by writing a 1 to the ${\tt TATOCINT}$ bit in the ${\bf GPTMICR}$ register.

Register 9: GPTM Interrupt Clear (GPTMICR), offset 0x024

This register is used to clear the status bits in the **GPTMRIS** and **GPTMMIS** registers. Writing a 1 to a bit clears the corresponding bit in the **GPTMRIS** and **GPTMMIS** registers.

GPTM Interrupt Clear (GPTMICR)

16/32-bit Timer 0 base: 0x4003.0000 16/32-bit Timer 1 base: 0x4003.1000 16/32-bit Timer 2 base: 0x4003.2000 16/32-bit Timer 3 base: 0x4003.3000 16/32-bit Timer 4 base: 0x4003.4000 16/32-bit Timer 5 base: 0x4003.5000 32/64-bit Wide Timer 0 base: 0x4003.7000 32/64-bit Wide Timer 1 base: 0x4004.C000 32/64-bit Wide Timer 2 base: 0x4004.D000 32/64-bit Wide Timer 3 base: 0x4004.D000 32/64-bit Wide Timer 4 base: 0x4004.D000 32/64-bit Wide Timer 5 base: 0x4004.F000

Offset 0x024
Type W1C, reset 0x0000.0000

_	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16
					1			reserved		, ,			1	1		WUECINT
Type	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	R/W
Reset	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0
	15	14	13	12	11	10	9	8	7	6	5	4	3	2	4	0
	15	14	13	12	- ''	10	. 9		- 1		5	4	<u> </u>		. '	
		rese	rved		TBMCINT	CBECINT	CBMCINT	TBTOCINT		reserved		TAMCINT	RTCCINT	CAECINT	CAMCINT	TATOCINT
Type	RO	RO	RO	RO	W1C	W1C	W1C	W1C	RO	RO	RO	W1C	W1C	W1C	W1C	W1C
Reset	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0

Bit/Field	Name	Туре	Reset	Description
31:17	reserved	RO	0x0000	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
16	WUECINT	R/W	0	32/64-Bit Wide GPTM Write Update Error Interrupt Clear
				Writing a 1 to this bit clears the WUERIS bit in the GPTMRIS register and the WUEMIS bit in the GPTMMIS register.
15:12	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
11	TBMCINT	W1C	0	GPTM Timer B Match Interrupt Clear
				Writing a 1 to this bit clears the TBMRIS bit in the GPTMRIS register and the TBMMIS bit in the GPTMMIS register.
10	CBECINT	W1C	0	GPTM Timer B Capture Mode Event Interrupt Clear
				Writing a 1 to this bit clears the CBERIS bit in the GPTMRIS register and the CBEMIS bit in the GPTMMIS register.
9	CBMCINT	W1C	0	GPTM Timer B Capture Mode Match Interrupt Clear
				Writing a 1 to this bit clears the CBMRIS bit in the GPTMRIS register and the CBMMIS bit in the GPTMMIS register.
8	TBTOCINT	W1C	0	GPTM Timer B Time-Out Interrupt Clear
				Writing a 1 to this bit clears the TBTORIS bit in the GPTMRIS register and the TBTOMIS bit in the GPTMMIS register.

Bit/Field	Name	Туре	Reset	Description
7:5	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
4	TAMCINT	W1C	0	GPTM Timer A Match Interrupt Clear
				Writing a 1 to this bit clears the TAMRIS bit in the GPTMRIS register and the TAMMIS bit in the GPTMMIS register.
3	RTCCINT	W1C	0	GPTM RTC Interrupt Clear
				Writing a 1 to this bit clears the RTCRIS bit in the GPTMRIS register and the RTCMIS bit in the GPTMMIS register.
2	CAECINT	W1C	0	GPTM Timer A Capture Mode Event Interrupt Clear
				Writing a 1 to this bit clears the CAERIS bit in the GPTMRIS register and the CAEMIS bit in the GPTMMIS register.
1	CAMCINT	W1C	0	GPTM Timer A Capture Mode Match Interrupt Clear
				Writing a 1 to this bit clears the CAMRIS bit in the GPTMRIS register and the CAMMIS bit in the GPTMMIS register.
0	TATOCINT	W1C	0	GPTM Timer A Time-Out Raw Interrupt
				Writing a 1 to this bit clears the TATORIS bit in the GPTMRIS register and the TATOMIS bit in the GPTMMIS register.

Register 10: GPTM Timer A Interval Load (GPTMTAILR), offset 0x028

When the timer is counting down, this register is used to load the starting count value into the timer. When the timer is counting up, this register sets the upper bound for the timeout event.

When a 16/32-bit GPTM is configured to one of the 32-bit modes, **GPTMTAILR** appears as a 32-bit register (the upper 16-bits correspond to the contents of the **GPTM Timer B Interval Load (GPTMTBILR)** register). In a 16-bit mode, the upper 16 bits of this register read as 0s and have no effect on the state of **GPTMTBILR**.


When a 32/64-bit Wide GPTM is configured to one of the 64-bit modes, **GPTMTAILR** contains bits 31:0 of the 64-bit count and the **GPTM Timer B Interval Load (GPTMTBILR)** register contains bits 63:32.

GPTM Timer A Interval Load (GPTMTAILR)

16/32-bit Timer 0 base: 0x4003.0000
16/32-bit Timer 1 base: 0x4003.1000
16/32-bit Timer 2 base: 0x4003.2000
16/32-bit Timer 3 base: 0x4003.3000
16/32-bit Timer 4 base: 0x4003.4000
16/32-bit Timer 5 base: 0x4003.5000
32/64-bit Wide Timer 0 base: 0x4003.6000
32/64-bit Wide Timer 1 base: 0x4003.7000
32/64-bit Wide Timer 2 base: 0x4004.C000
32/64-bit Wide Timer 3 base: 0x4004.D000
32/64-bit Wide Timer 4 base: 0x4004.D000

32/64-bit Wide Timer 5 base: 0x4004.F000

Offset 0x028 Type R/W, reset 0xFFFF.FFF



Bit/Field	Name	Туре	Reset	Description
31:0	TAILR	R/W	0xFFFF.FFFF	GPTM Timer A Interval Load Register

Writing this field loads the counter for Timer A. A read returns the current value of $\mbox{\bf GPTMTAILR}.$

Register 11: GPTM Timer B Interval Load (GPTMTBILR), offset 0x02C


When the timer is counting down, this register is used to load the starting count value into the timer. When the timer is counting up, this register sets the upper bound for the timeout event.

When a 16/32-bit GPTM is configured to one of the 32-bit modes, the contents of bits 15:0 in this register are loaded into the upper 16 bits of the GPTMTAILR register. Reads from this register return the current value of Timer B and writes are ignored. In a 16-bit mode, bits 15:0 are used for the load value. Bits 31:16 are reserved in both cases.

When a 32/64-bit Wide GPTM is configured to one of the 64-bit modes, GPTMTAILR contains bits 31:0 of the 64-bit count and the **GPTMTBILR** register contains bits 63:32.

GPTM Timer B Interval Load (GPTMTBILR)

16/32-bit Timer 0 base: 0x4003.0000 16/32-bit Timer 1 base: 0x4003.1000 16/32-bit Timer 2 base: 0x4003.2000 16/32-bit Timer 3 base: 0x4003.3000 16/32-bit Timer 4 base: 0x4003.4000 16/32-bit Timer 5 base: 0x4003.5000 32/64-bit Wide Timer 0 base: 0x4003.6000 32/64-bit Wide Timer 1 base: 0x4003.7000 32/64-bit Wide Timer 2 base: 0x4004.C000 32/64-bit Wide Timer 3 base: 0x4004.D000 32/64-bit Wide Timer 4 base: 0x4004.E000 32/64-bit Wide Timer 5 base: 0x4004.F000 Offset 0x02C Type R/W, reset -



Bit/Field	Name	Type	Reset	Description
31:0	TBILR	R/W	0x0000.FFFF	GPTM Timer B Interval Load Register

(for 16/32-bit) 0xFFFF.FFFF (for 32/64-bit)

Writing this field loads the counter for Timer B. A read returns the current value of **GPTMTBILR**.

When a 16/32-bit GPTM is in 32-bit mode, writes are ignored, and reads return the current value of GPTMTBILR.

Register 12: GPTM Timer A Match (GPTMTAMATCHR), offset 0x030

This register is loaded with a match value. Interrupts can be generated when the timer value is equal to the value in this register in one-shot or periodic mode.

In Edge-Count mode, this register along with **GPTMTAILR**, determines how many edge events are counted. The total number of edge events counted is equal to the value in **GPTMTAILR** minus this value. Note that in edge-count mode, when executing an up-count, the value of **GPTMTnPR** and **GPTMTnILR** must be greater than the value of **GPTMTnPMR** and **GPTMTnMATCHR**.

In PWM mode, this value along with **GPTMTAILR**, determines the duty cycle of the output PWM signal.

When a 16/32-bit GPTM is configured to one of the 32-bit modes, **GPTMTAMATCHR** appears as a 32-bit register (the upper 16-bits correspond to the contents of the **GPTM Timer B Match (GPTMTBMATCHR)** register). In a 16-bit mode, the upper 16 bits of this register read as 0s and have no effect on the state of **GPTMTBMATCHR**.


When a 32/64-bit Wide GPTM is configured to one of the 64-bit modes, **GPTMTAMATCHR** contains bits 31:0 of the 64-bit match value and the **GPTM Timer B Match (GPTMTBMATCHR)** register contains bits 63:32.

GPTM Timer A Match (GPTMTAMATCHR)

16/32-bit Timer 0 base: 0x4003.0000
16/32-bit Timer 1 base: 0x4003.1000
16/32-bit Timer 2 base: 0x4003.2000
16/32-bit Timer 3 base: 0x4003.3000
16/32-bit Timer 4 base: 0x4003.4000
16/32-bit Timer 5 base: 0x4003.5000
32/64-bit Wide Timer 0 base: 0x4003.6000
32/64-bit Wide Timer 1 base: 0x4003.7000
32/64-bit Wide Timer 2 base: 0x4004.C000
32/64-bit Wide Timer 3 base: 0x4004.D000
32/64-bit Wide Timer 4 base: 0x4004.D000

32/64-bit Wide Timer 4 base: 0x4004.E000 32/64-bit Wide Timer 5 base: 0x4004.F000

Offset 0x030 Type R/W, reset 0xFFFF.FFF



Bit/Field Name Type Reset Description

31:0 TAMR R/W 0xFFF.FFFF GPTM Timer A Match Register

This value is compared to the **GPTMTAR** register to determine match events.

Register 13: GPTM Timer B Match (GPTMTBMATCHR), offset 0x034

This register is loaded with a match value. Interrupts can be generated when the timer value is equal to the value in this register in one-shot or periodic mode.

In Edge-Count mode, this register along with **GPTMTBILR** determines how many edge events are counted. The total number of edge events counted is equal to the value in **GPTMTBILR** minus this value. Note that in edge-count mode, when executing an up-count, the value of **GPTMTnPR** and **GPTMTnILR** must be greater than the value of **GPTMTnPMR** and **GPTMTnMATCHR**.


In PWM mode, this value along with **GPTMTBILR**, determines the duty cycle of the output PWM signal.

When a 16/32-bit GPTM is configured to one of the 32-bit modes, the contents of bits 15:0 in this register are loaded into the upper 16 bits of the **GPTMTAMATCHR** register. Reads from this register return the current match value of Timer B and writes are ignored. In a 16-bit mode, bits 15:0 are used for the match value. Bits 31:16 are reserved in both cases.

When a 32/64-bit Wide GPTM is configured to one of the 64-bit modes, **GPTMTAMATCHR** contains bits 31:0 of the 64-bit match value and the **GPTMTBMATCHR** register contains bits 63:32.

GPTM Timer B Match (GPTMTBMATCHR)

16/32-bit Timer 0 base: 0x4003.0000
16/32-bit Timer 1 base: 0x4003.1000
16/32-bit Timer 2 base: 0x4003.2000
16/32-bit Timer 3 base: 0x4003.3000
16/32-bit Timer 4 base: 0x4003.4000
16/32-bit Timer 5 base: 0x4003.5000
32/64-bit Wide Timer 0 base: 0x4003.6000
32/64-bit Wide Timer 1 base: 0x4003.7000
32/64-bit Wide Timer 2 base: 0x4004.000
32/64-bit Wide Timer 3 base: 0x4004.000
32/64-bit Wide Timer 3 base: 0x4004.000
32/64-bit Wide Timer 4 base: 0x4004.000
32/64-bit Wide Timer 5 base: 0x4004.F000
07fset 0x034
Type R/W, reset -



Bit/Field Name Type Reset Description

31:0 TBMR R/W 0x0000.FFFF GPTM Timer B Match Register

(for 16/32-bit) This value is compared to the **GPTMTBR** register to determine match events.

Register 14: GPTM Timer A Prescale (GPTMTAPR), offset 0x038

This register allows software to extend the range of the timers when they are used individually. When in one-shot or periodic down count modes, this register acts as a true prescaler for the timer counter. When acting as a true prescaler, the prescaler counts down to 0 before the value in the **GPTMTAR** and **GPTMTAV** registers are incremented. In all other individual/split modes, this register is a linear extension of the upper range of the timer counter, holding bits 23:16 in the 16-bit modes of the 16/32-bit GPTM and bits 47:32 in the 32-bit modes of the 32/64-bit Wide GPTM.

GPTM Timer A Prescale (GPTMTAPR)

16/32-bit Timer 0 base: 0x4003.0000
16/32-bit Timer 1 base: 0x4003.1000
16/32-bit Timer 2 base: 0x4003.2000
16/32-bit Timer 3 base: 0x4003.3000
16/32-bit Timer 4 base: 0x4003.4000
16/32-bit Timer 5 base: 0x4003.5000
32/64-bit Wide Timer 0 base: 0x4003.6000
32/64-bit Wide Timer 1 base: 0x4003.7000
32/64-bit Wide Timer 2 base: 0x4004.C000
32/64-bit Wide Timer 3 base: 0x4004.D000
32/64-bit Wide Timer 4 base: 0x4004.E000
32/64-bit Wide Timer 5 base: 0x4004.F000
Offset 0x038


Name

Type

Reset

Type R/W, reset 0x0000.0000

Bit/Field



		.,,,,,		
31:16	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
15:8	TAPSRH	R/W	0x00	GPTM Timer A Prescale High Byte The register loads this value on a write. A read returns the current value of the register.
				For the 16/32-bit GPTM, this field is reserved. For the 32/64-bit Wide GPTM, this field contains the upper 8-bits of the 16-bit prescaler.
				Refer to Table 11-5 on page 711 for more details and an example.
7:0	TAPSR	R/W	0x00	GPTM Timer A Prescale

Description

The register loads this value on a write. A read returns the current value of the register.

For the 16/32-bit GPTM, this field contains the entire 8-bit prescaler. For the 32/64-bit Wide GPTM, this field contains the lower 8-bits of the 16-bit prescaler.

Refer to Table 11-5 on page 711 for more details and an example.


Register 15: GPTM Timer B Prescale (GPTMTBPR), offset 0x03C

This register allows software to extend the range of the timers when they are used individually. When in one-shot or periodic down count modes, this register acts as a true prescaler for the timer counter. When acting as a true prescaler, the prescaler counts down to 0 before the value in the **GPTMTBR** and **GPTMTBV** registers are incremented. In all other individual/split modes, this register is a linear extension of the upper range of the timer counter, holding bits 23:16 in the 16-bit modes of the 16/32-bit GPTM and bits 47:32 in the 32-bit modes of the 32/64-bit Wide GPTM.

GPTM Timer B Prescale (GPTMTBPR)

16/32-bit Timer 0 base: 0x4003.0000
16/32-bit Timer 1 base: 0x4003.1000
16/32-bit Timer 2 base: 0x4003.2000
16/32-bit Timer 3 base: 0x4003.3000
16/32-bit Timer 4 base: 0x4003.4000
16/32-bit Timer 5 base: 0x4003.5000
32/64-bit Wide Timer 0 base: 0x4003.6000
32/64-bit Wide Timer 1 base: 0x4003.7000
32/64-bit Wide Timer 2 base: 0x4004.C000
32/64-bit Wide Timer 3 base: 0x4004.D000
32/64-bit Wide Timer 4 base: 0x4004.E000
32/64-bit Wide Timer 5 base: 0x4004.F000
Offset 0x03C

Type R/W, reset 0x0000.0000



Bit/Field	Name	Type	Reset	Description
31:16	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
15:8	TBPSRH	R/W	0x00	GPTM Timer B Prescale High Byte
				The register loads this value on a write. A read returns the current value of the register.
				For the 16/32-bit GPTM, this field is reserved. For the 32/64-bit Wide GPTM, this field contains the upper 8-bits of the 16-bit prescaler.
				Refer to Table 11-5 on page 711 for more details and an example.
7:0	TBPSR	R/W	0x00	GPTM Timer B Prescale

The register loads this value on a write. A read returns the current value of this register.

For the 16/32-bit GPTM, this field contains the entire 8-bit prescaler. For the 32/64-bit Wide GPTM, this field contains the lower 8-bits of the 16-bit prescaler.

Refer to Table 11-5 on page 711 for more details and an example.

Register 16: GPTM TimerA Prescale Match (GPTMTAPMR), offset 0x040

This register allows software to extend the range of the **GPTMTAMATCHR** when the timers are used individually. This register holds bits 23:16 in the 16-bit modes of the 16/32-bit GPTM and bits 47:32 in the 32-bit modes of the 32/64-bit Wide GPTM.

GPTM TimerA Prescale Match (GPTMTAPMR)


Nama

16/32-bit Timer 0 base: 0x4003.0000
16/32-bit Timer 1 base: 0x4003.1000
16/32-bit Timer 2 base: 0x4003.2000
16/32-bit Timer 3 base: 0x4003.3000
16/32-bit Timer 4 base: 0x4003.4000
16/32-bit Timer 5 base: 0x4003.5000
32/64-bit Wide Timer 0 base: 0x4003.6000
32/64-bit Wide Timer 1 base: 0x4003.7000
32/64-bit Wide Timer 2 base: 0x4004.C000
32/64-bit Wide Timer 3 base: 0x4004.D000
32/64-bit Wide Timer 4 base: 0x4004.E000
32/64-bit Wide Timer 5 base: 0x4004.E000

Offset 0x040

Rit/Field

Type R/W, reset 0x0000.0000



Type

Pacat

Divi leiu	IName	Type	Neset	Description
31:16	reserved	RO	0x0000	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
15:8	TAPSMRH	R/W	0x00	GPTM Timer A Prescale Match High Byte This value is used alongside GPTMTAMATCHR to detect timer match events while using a prescaler.
				For the 16/32-bit GPTM, this field is reserved. For the 32/64-bit Wide GPTM, this field contains the upper 8-bits of the 16-bit prescale match value.
7:0	TAPSMR	R/W	0x00	GPTM TimerA Prescale Match

Description

This value is used alongside **GPTMTAMATCHR** to detect timer match events while using a prescaler.

For the 16/32-bit GPTM, this field contains the entire 8-bit prescaler match value. For the 32/64-bit Wide GPTM, this field contains the lower 8-bits of the 16-bit prescaler match value.

Register 17: GPTM TimerB Prescale Match (GPTMTBPMR), offset 0x044

This register allows software to extend the range of the **GPTMTBMATCHR** when the timers are used individually. This register holds bits 23:16 in the 16-bit modes of the 16/32-bit GPTM and bits 47:32 in the 32-bit modes of the 32/64-bit Wide GPTM.

GPTM TimerB Prescale Match (GPTMTBPMR)

Name

Type


Reset

16/32-bit Timer 0 base: 0x4003.0000
16/32-bit Timer 1 base: 0x4003.1000
16/32-bit Timer 2 base: 0x4003.2000
16/32-bit Timer 3 base: 0x4003.3000
16/32-bit Timer 4 base: 0x4003.4000
16/32-bit Timer 5 base: 0x4003.5000
32/64-bit Wide Timer 0 base: 0x4003.6000
32/64-bit Wide Timer 1 base: 0x4003.7000
32/64-bit Wide Timer 2 base: 0x4004.C000
32/64-bit Wide Timer 3 base: 0x4004.D000
32/64-bit Wide Timer 4 base: 0x4004.D000

32/64-bit Wide Timer 5 base: 0x4004.F000 Offset 0x044

Type R/W, reset 0x0000.0000

Bit/Field



		71		•
31:16	reserved	RO	0x0000	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
15:8	TBPSMRH	R/W	0x00	GPTM Timer B Prescale Match High Byte This value is used alongside GPTMTBMATCHR to detect timer match events while using a prescaler.
				For the 16/32-bit GPTM, this field is reserved. For the 32/64-bit Wide GPTM, this field contains the upper 8-bits of the 16-bit prescale match value.
7:0	TBPSMR	R/W	0x00	GPTM TimerB Prescale Match

Description

This value is used alongside **GPTMTBMATCHR** to detect timer match events while using a prescaler.

For the 16/32-bit GPTM, this field contains the entire 8-bit prescaler match value. For the 32/64-bit Wide GPTM, this field contains the lower 8-bits of the 16-bit prescaler match value.

Register 18: GPTM Timer A (GPTMTAR), offset 0x048

This register shows the current value of the Timer A counter in all cases except for Input Edge Count and Time modes. In the Input Edge Count mode, this register contains the number of edges that have occurred. In the Input Edge Time mode, this register contains the time at which the last edge event took place.


When a 16/32-bit GPTM is configured to one of the 32-bit modes, **GPTMTAR** appears as a 32-bit register (the upper 16-bits correspond to the contents of the **GPTM Timer B (GPTMTBR)** register). In the16-bit Input Edge Count, Input Edge Time, and PWM modes, bits 15:0 contain the value of the counter and bits 23:16 contain the value of the prescaler, which is the upper 8 bits of the count. Bits 31:24 always read as 0. To read the value of the prescaler in 16-bit One-Shot and Periodic modes, read bits [23:16] in the **GPTMTAV** register.


When a 32/64-bit Wide GPTM is configured to one of the 64-bit modes, **GPTMTAR** contains bits 31:0 of the 64-bit timer value and the **GPTM Timer B (GPTMTBR)** register contains bits 63:32. In a 32-bit mode, the value of the prescaler is stored in the **GPTM Timer A Prescale Snapshot (GPTMTAPS)** register.

GPTM Timer A (GPTMTAR)

16/32-bit Timer 0 base: 0x4003.0000
16/32-bit Timer 1 base: 0x4003.1000
16/32-bit Timer 2 base: 0x4003.2000
16/32-bit Timer 3 base: 0x4003.3000
16/32-bit Timer 4 base: 0x4003.4000
16/32-bit Timer 5 base: 0x4003.5000
32/64-bit Wide Timer 0 base: 0x4003.6000
32/64-bit Wide Timer 1 base: 0x4003.7000
32/64-bit Wide Timer 2 base: 0x4004.C000
32/64-bit Wide Timer 3 base: 0x4004.D000
32/64-bit Wide Timer 4 base: 0x4004.D000
32/64-bit Wide Timer 5 base: 0x4004.F000

Offset 0x048 Type RO, reset 0xFFFF.FFF





A read returns the current value of the **GPTM Timer A Count Register**, in all cases except for Input Edge Count and Time modes. In the Input Edge Count mode, this register contains the number of edges that have occurred. In the Input Edge Time mode, this register contains the time at which the last edge event took place.

Register 19: GPTM Timer B (GPTMTBR), offset 0x04C

This register shows the current value of the Timer B counter in all cases except for Input Edge Count and Time modes. In the Input Edge Count mode, this register contains the number of edges that have occurred. In the Input Edge Time mode, this register contains the time at which the last edge event took place.


When a 16/32-bit GPTM is configured to one of the 32-bit modes, the contents of bits 15:0 in this register are loaded into the upper 16 bits of the **GPTMTAR** register. Reads from this register return the current value of Timer B. In a 16-bit mode, bits 15:0 contain the value of the counter and bits 23:16 contain the value of the prescaler in Input Edge Count, Input Edge Time, and PWM modes, which is the upper 8 bits of the count. Bits 31:24 always read as 0. To read the value of the prescaler in 16-bit One-Shot and Periodic modes, read bits [23:16] in the **GPTMTBV** register.

When a 32/64-bit Wide GPTM is configured to one of the 64-bit modes, **GPTMTAR** contains bits 31:0 of the 64-bit timer value and the GPTM Timer B (GPTMTBR) register contains bits 63:32. In a 32-bit mode, the value of the prescaler is stored in the GPTM Timer B Prescale Snapshot (GPTMTBPS) register.

GPTM Timer B (GPTMTBR)

16/32-bit Timer 0 base: 0x4003.0000 16/32-bit Timer 1 base: 0x4003.1000 16/32-bit Timer 2 base: 0x4003.2000 16/32-bit Timer 3 base: 0x4003.3000 16/32-bit Timer 4 base: 0x4003.4000 16/32-bit Timer 5 base: 0x4003 5000 32/64-bit Wide Timer 0 base: 0x4003.6000 32/64-bit Wide Timer 1 base: 0x4003.7000 32/64-bit Wide Timer 2 base: 0x4004.C000 32/64-bit Wide Timer 3 base: 0x4004.D000 32/64-bit Wide Timer 4 base: 0x4004.E000 32/64-bit Wide Timer 5 base: 0x4004.F000





Bit/Field	Name	Туре	Reset	Description
31:0	TBR	RO	0x0000.FFFF	GPTM Timer B Register

(for 32/64-bit)

(for 16/32-bit) A read returns the current value of the GPTM Timer B Count Register, in all cases except for Input Edge Count and Time modes. In the Input Edge Count mode, this register contains the number of edges that have occurred. In the Input Edge Time mode, this register contains the time at which the last edge event took place.

Register 20: GPTM Timer A Value (GPTMTAV), offset 0x050

When read, this register shows the current, free-running value of Timer A in all modes. Software can use this value to determine the time elapsed between an interrupt and the ISR entry when using the snapshot feature with the periodic operating mode. When written, the value written into this register is loaded into the **GPTMTAR** register on the next clock cycle.


When a 16/32-bit GPTM is configured to one of the 32-bit modes, **GPTMTAV** appears as a 32-bit register (the upper 16-bits correspond to the contents of the **GPTM Timer B Value (GPTMTBV)** register). In a 16-bit mode, bits 15:0 contain the value of the counter and bits 23:16 contain the current, free-running value of the prescaler, which is the upper 8 bits of the count in Input Edge Count, Input Edge Time, PWM and one-shot or periodic up count modes. In one-shot or periodic down count modes, the prescaler stored in 23:16 is a true prescaler, meaning bits 23:16 count down before decrementing the value in bits 15:0. The prescaler in bits 31:24 always reads as 0.

When a 32/64-bit Wide GPTM is configured to one of the 64-bit modes, GPTMTAV contains bits 31:0 of the 64-bit timer value and the GPTM Timer B Value (GPTMTBV) register contains bits 63:32. In a 32-bit mode, the current, free-running value of the prescaler is stored in the **GPTM Timer** A Prescale Value (GPTMTAPV) register.mint

GPTM Timer A Value (GPTMTAV)

16/32-bit Timer 0 base: 0x4003.0000 16/32-bit Timer 1 base: 0x4003.1000 16/32-bit Timer 2 base: 0x4003.2000 16/32-bit Timer 3 base: 0x4003.3000 16/32-bit Timer 4 base: 0x4003.4000 16/32-bit Timer 5 base: 0x4003.5000 32/64-bit Wide Timer 0 base: 0x4003.6000 32/64-bit Wide Timer 1 base: 0x4003.7000 32/64-bit Wide Timer 2 base: 0x4004.C000 32/64-bit Wide Timer 3 base: 0x4004.D000 32/64-bit Wide Timer 4 base: 0x4004 F000 32/64-bit Wide Timer 5 base: 0x4004.F000 Offset 0x050

Type RW, reset 0xFFFF.FFFF





A read returns the current, free-running value of Timer A in all modes. When written, the value written into this register is loaded into the **GPTMTAR** register on the next clock cycle.

In 16-bit mode, only the lower 16-bits of the GPTMTAV register can be written with a new value. Writes to the prescaler bits have no effect.

Register 21: GPTM Timer B Value (GPTMTBV), offset 0x054

When read, this register shows the current, free-running value of Timer B in all modes. Software can use this value to determine the time elapsed between an interrupt and the ISR entry. When written, the value written into this register is loaded into the **GPTMTBR** register on the next clock cycle.


When a 16/32-bit GPTM is configured to one of the 32-bit modes, the contents of bits 15:0 in this register are loaded into the upper 16 bits of the **GPTMTAV** register. Reads from this register return the current free-running value of Timer B. In a 16-bit mode, bits 15:0 contain the value of the counter and bits 23:16 contain the current, free-running value of the prescaler, which is the upper 8 bits of the count in Input Edge Count, Input Edge Time, PWM and one-shot or periodic up count modes. In one-shot or periodic down count modes, the prescaler stored in 23:16 is a true prescaler, meaning bits 23:16 count down before decrementing the value in bits 15:0. The prescaler in bits 31:24 always reads as 0.

When a 32/64-bit Wide GPTM is configured to one of the 64-bit modes, GPTMTBV contains bits 63:32 of the 64-bit timer value and the GPTM Timer A Value (GPTMTAV) register contains bits 31:0. In a 32-bit mode, the current, free-running value of the prescaler is stored in the **GPTM Timer** B Prescale Value (GPTMTBPV) register.

GPTM Timer B Value (GPTMTBV)

16/32-bit Timer 0 base: 0x4003.0000 16/32-bit Timer 1 base: 0x4003.1000 16/32-bit Timer 2 base: 0x4003.2000 16/32-bit Timer 3 base: 0x4003.3000 16/32-bit Timer 4 base: 0x4003.4000 16/32-bit Timer 5 base: 0x4003 5000 32/64-bit Wide Timer 0 base: 0x4003.6000 32/64-bit Wide Timer 1 base: 0x4003.7000 32/64-bit Wide Timer 2 base: 0x4004.C000 32/64-bit Wide Timer 3 base: 0x4004.D000 32/64-bit Wide Timer 4 base: 0x4004.E000 32/64-bit Wide Timer 5 base: 0x4004.F000

Offset 0x054 Type RW, reset



Bit/Field Name Type Reset Description 31:0 TBV RW 0x0000.FFFF GPTM Timer B Value

(for 32/64-bit)

(for 16/32-bit) A read returns the current, free-running value of Timer A in all modes. When written, the value written into this register is loaded into the

GPTMTAR register on the next clock cycle.

In 16-bit mode, only the lower 16-bits of the GPTMTBV Note: register can be written with a new value. Writes to the prescaler bits have no effect.

Register 22: GPTM RTC Predivide (GPTMRTCPD), offset 0x058


This register provides the current RTC predivider value when the timer is operating in RTC mode. Software must perform an atomic access with consecutive reads of the **GPTMTAR**, **GPTMTBR**, and **GPTMRTCPD** registers, see Figure 11-2 on page 712 for more information.

GPTM RTC Predivide (GPTMRTCPD)

16/32-bit Timer 0 base: 0x4003.0000
16/32-bit Timer 1 base: 0x4003.1000
16/32-bit Timer 2 base: 0x4003.2000
16/32-bit Timer 3 base: 0x4003.3000
16/32-bit Timer 4 base: 0x4003.4000
16/32-bit Timer 5 base: 0x4003.5000
32/64-bit Wide Timer 0 base: 0x4003.6000
32/64-bit Wide Timer 1 base: 0x4004.0000
32/64-bit Wide Timer 2 base: 0x4004.0000
32/64-bit Wide Timer 3 base: 0x4004.0000
32/64-bit Wide Timer 4 base: 0x4004.E000
32/64-bit Wide Timer 5 base: 0x4004.F000

Offset 0x058

Type RO, reset 0x0000.7FFF



E	Bit/Field	Name	Туре	Reset	Description
	31:16	reserved	RO	0x0000	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
	15:0	RTCPD	RO 0	x0000 7FFF	RTC Predivide Counter Value

The current RTC predivider value when the timer is operating in RTC mode. This field has no meaning in other timer modes.


Register 23: GPTM Timer A Prescale Snapshot (GPTMTAPS), offset 0x05C

For the 32/64-bit Wide GPTM, this register shows the current value of the Timer A prescaler in the 32-bit modes. This register is ununsed in 16/32-bit GPTM mode.

GPTM Timer A Prescale Snapshot (GPTMTAPS)

16/32-bit Timer 0 base: 0x4003.0000
16/32-bit Timer 1 base: 0x4003.1000
16/32-bit Timer 2 base: 0x4003.2000
16/32-bit Timer 3 base: 0x4003.3000
16/32-bit Timer 4 base: 0x4003.4000
16/32-bit Timer 5 base: 0x4003.5000
32/64-bit Wide Timer 0 base: 0x4003.6000
32/64-bit Wide Timer 1 base: 0x4003.7000
32/64-bit Wide Timer 2 base: 0x4004.0000
32/64-bit Wide Timer 3 base: 0x4004.D000
32/64-bit Wide Timer 4 base: 0x4004.E000
32/64-bit Wide Timer 5 base: 0x4004.F000

Offset 0x05C Type RO, reset 0x0000.0000



Bit/Field	Name	Type	Reset	Description
31:16	reserved	RO	0x0000	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
15:0	PSS	RO	0x0000	GPTM Timer A Prescaler Snapshot


A read returns the current value of the GPTM Timer A Prescaler.

Register 24: GPTM Timer B Prescale Snapshot (GPTMTBPS), offset 0x060

For the 32/64-bit Wide GPTM, this register shows the current value of the Timer B prescaler in the 32-bit modes. This register is ununsed in 16/32-bit GPTM mode.

GPTM Timer B Prescale Snapshot (GPTMTBPS)

16/32-bit Timer 0 base: 0x4003.0000 16/32-bit Timer 1 base: 0x4003.1000 16/32-bit Timer 2 base: 0x4003.2000 16/32-bit Timer 3 base: 0x4003.3000 16/32-bit Timer 4 base: 0x4003.4000 16/32-bit Timer 5 base: 0x4003.5000 32/64-bit Wide Timer 0 base: 0x4003.6000 32/64-bit Wide Timer 1 base: 0x4003.7000 32/64-bit Wide Timer 2 base: 0x4004.C000 32/64-bit Wide Timer 3 base: 0x4004.D000 32/64-bit Wide Timer 4 base: 0x4004.E000 32/64-bit Wide Timer 5 base: 0x4004.F000 Offset 0x060 Type RO, reset 0x0000.0000



Bit/Field	Name	Type	Reset	Description
31:16	reserved	RO	0x0000	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
15:0	PSS	RO	0x0000	GPTM Timer A Prescaler Value

A read returns the current value of the GPTM Timer A Prescaler.

Register 25: GPTM Timer A Prescale Value (GPTMTAPV), offset 0x064


For the 32/64-bit Wide GPTM, this register shows the current free-running value of the Timer A prescaler in the 32-bit modes. Software can use this value in conjunction with the GPTMTAV register to determine the time elapsed between an interrupt and the ISR entry. This register is ununsed in 16/32-bit GPTM mode.

GPTM Timer A Prescale Value (GPTMTAPV)

16/32-bit Timer 0 base: 0x4003.0000 16/32-bit Timer 1 base: 0x4003.1000 16/32-bit Timer 2 base: 0x4003.2000 16/32-bit Timer 3 base: 0x4003.3000 16/32-bit Timer 4 base: 0x4003.4000 16/32-bit Timer 5 base: 0x4003.5000 32/64-bit Wide Timer 0 base: 0x4003.6000 32/64-bit Wide Timer 1 base: 0x4003.7000 32/64-bit Wide Timer 2 base: 0x4004.C000 32/64-bit Wide Timer 3 base: 0x4004.D000 32/64-bit Wide Timer 4 base: 0x4004.E000 32/64-bit Wide Timer 5 base: 0x4004.F000

Offset 0x064

Type RO, reset 0x0000.0000



Bit/Field	Name	Type	Reset	Description
31:16	reserved	RO	0x0000	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
15:0	PSV	RO	0x0000	GPTM Timer A Prescaler Value

A read returns the current, free-running value of the Timer A prescaler.

Register 26: GPTM Timer B Prescale Value (GPTMTBPV), offset 0x068


For the 32/64-bit Wide GPTM, this register shows the current free-running value of the Timer B prescaler in the 32-bit modes. Software can use this value in conjunction with the GPTMTBV register to determine the time elapsed between an interrupt and the ISR entry. This register is ununsed in 16/32-bit GPTM mode.

GPTM Timer B Prescale Value (GPTMTBPV)

16/32-bit Timer 0 base: 0x4003.0000 16/32-bit Timer 1 base: 0x4003.1000 16/32-bit Timer 2 base: 0x4003.2000 16/32-bit Timer 3 base: 0x4003.3000 16/32-bit Timer 4 base: 0x4003.4000 16/32-bit Timer 5 base: 0x4003.5000 32/64-bit Wide Timer 0 base: 0x4003.6000 32/64-bit Wide Timer 1 base: 0x4003.7000 32/64-bit Wide Timer 2 base: 0x4004.C000 32/64-bit Wide Timer 3 base: 0x4004.D000 32/64-bit Wide Timer 4 base: 0x4004.E000 32/64-bit Wide Timer 5 base: 0x4004.F000

Offset 0x068

Type RO, reset 0x0000.0000



Bit/Field	Name	Type	Reset	Description
31:16	reserved	RO	0x0000	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
15:0	PSV	RO	0x0000	GPTM Timer B Prescaler Value

A read returns the current, free-running value of the Timer A prescaler.


Register 27: GPTM Peripheral Properties (GPTMPP), offset 0xFC0

The **GPTMPP** register provides information regarding the properties of the General-Purpose Timer module.

GPTM Peripheral Properties (GPTMPP)

16/32-bit Timer 0 base: 0x4003.0000 16/32-bit Timer 1 base: 0x4003.1000 16/32-bit Timer 2 base: 0x4003.2000 16/32-bit Timer 3 base: 0x4003.3000 16/32-bit Timer 4 base: 0x4003.4000 16/32-bit Timer 5 base: 0x4003.5000 32/64-bit Wide Timer 0 base: 0x4003.6000 32/64-bit Wide Timer 1 base: 0x4003.7000 32/64-bit Wide Timer 2 base: 0x4004.C000 32/64-bit Wide Timer 3 base: 0x4004.D000 32/64-bit Wide Timer 4 base: 0x4004.E000 32/64-bit Wide Timer 5 base: 0x4004.F000

Offset 0xFC0 Type RO, reset 0x0000.0000



Bit/Field	Name	Туре	Reset	Description
31:4	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
3:0	SIZE	RO	0x0	Count Size

- Timer A and Timer B counters are 16 bits each with an 8-bit prescale counter.
- Timer A and Timer B counters are 32 bits each with a 16-bit prescale counter.

12 Watchdog Timers

A watchdog timer can generate a non-maskable interrupt (NMI), a regular interrupt or a reset when a time-out value is reached. The watchdog timer is used to regain control when a system has failed due to a software error or due to the failure of an external device to respond in the expected way. The LM4F232H5QC microcontroller has two Watchdog Timer Modules, one module is clocked by the system clock (Watchdog Timer 0) and the other (Watchdog Timer 1) is clocked by the PIOSC The two modules are identical except that WDT1 is in a different clock domain, and therefore requires synchronizers. As a result, WDT1 has a bit defined in the **Watchdog Timer Control (WDTCTL)** register to indicate when a write to a WDT1 register is complete. Software can use this bit to ensure that the previous access has completed before starting the next access.


The Stellaris[®] LM4F232H5QC controller has two Watchdog Timer modules with the following features:

- 32-bit down counter with a programmable load register
- Separate watchdog clock with an enable
- Programmable interrupt generation logic with interrupt masking and optional NMI function
- Lock register protection from runaway software
- Reset generation logic with an enable/disable
- User-enabled stalling when the microcontroller asserts the CPU Halt flag during debug

The Watchdog Timer can be configured to generate an interrupt to the controller on its first time-out, and to generate a reset signal on its second time-out. Once the Watchdog Timer has been configured, the lock register can be written to prevent the timer configuration from being inadvertently altered.

12.1 Block Diagram

Figure 12-1. WDT Module Block Diagram



12.2 Functional Description

The Watchdog Timer module generates the first time-out signal when the 32-bit counter reaches the zero state after being enabled; enabling the counter also enables the watchdog timer interrupt. The watchdog interrupt can be programmed to be an non-maskable interrupt (NMI) using the INTTYPE bit in the WDTCTL register. After the first time-out event, the 32-bit counter is re-loaded with the value of the Watchdog Timer Load (WDTLOAD) register, and the timer resumes counting down from that value. Once the Watchdog Timer has been configured, the Watchdog Timer Lock (WDTLOCK) register is written, which prevents the timer configuration from being inadvertently altered by software.

If the timer counts down to its zero state again before the first time-out interrupt is cleared, and the reset signal has been enabled by setting the RESEN bit in the **WDTCTL** register, the Watchdog timer asserts its reset signal to the system. If the interrupt is cleared before the 32-bit counter reaches its second time-out, the 32-bit counter is loaded with the value in the **WDTLOAD** register, and counting resumes from that value.

If **WDTLOAD** is written with a new value while the Watchdog Timer counter is counting, then the counter is loaded with the new value and continues counting.

Writing to **WDTLOAD** does not clear an active interrupt. An interrupt must be specifically cleared by writing to the **Watchdog Interrupt Clear (WDTICR)** register.

The Watchdog module interrupt and reset generation can be enabled or disabled as required. When the interrupt is re-enabled, the 32-bit counter is preloaded with the load register value and not its last state.

12.2.1 Register Access Timing

Because the Watchdog Timer 1 module has an independent clocking domain, its registers must be written with a timing gap between accesses. Software must guarantee that this delay is inserted between back-to-back writes to WDT1 registers or between a write followed by a read to the registers. The timing for back-to-back reads from the WDT1 module has no restrictions. The WRC bit in the **Watchdog Control (WDTCTL)** register for WDT1 indicates that the required timing gap has elapsed. This bit is cleared on a write operation and set once the write completes, indicating to software that another write or read may be started safely. Software should poll **WDTCTL** for WRC=1 prior to accessing another register. Note that WDT0 does not have this restriction as it runs off the system clock.

12.3 Initialization and Configuration

To use the WDT, its peripheral clock must be enabled by setting the Rn bit in the **Watchdog Timer Run Mode Clock Gating Control (RCGCWD)** register, see page 327.

The Watchdog Timer is configured using the following sequence:

- 1. Load the **WDTLOAD** register with the desired timer load value.
- 2. If WDT1, wait for the WRC bit in the WDTCTL register to be set.
- If the Watchdog is configured to trigger system resets, set the RESEN bit in the WDTCTL register.
- 4. If WDT1, wait for the WRC bit in the WDTCTL register to be set.
- Set the INTEN bit in the WDTCTL register to enable the Watchdog and lock the control register.

If software requires that all of the watchdog registers are locked, the Watchdog Timer module can be fully locked by writing any value to the **WDTLOCK** register. To unlock the Watchdog Timer, write a value of 0x1ACC.E551.

To service the watchdog, periodically reload the count value into the **WDTLOAD** register to restart the count. The interrupt can be enabled using the INTEN bit in the **WDTCTL** register to allow the processor to attempt corrective action if the watchdog is not serviced often enough. The RESEN bit in **WDTCTL** can be set so that the system resets if the failure is not recoverable using the ISR.

12.4 Register Map

Table 12-1 on page 777 lists the Watchdog registers. The offset listed is a hexadecimal increment to the register's address, relative to the Watchdog Timer base address:

■ WDT0: 0x4000.0000 ■ WDT1: 0x4000.1000

Note that the Watchdog Timer module clock must be enabled before the registers can be programmed (see page 327).

Table 12-1. Watchdog Timers Register Map

Offset	Name	Туре	Reset	Description	See page
0x000	WDTLOAD	R/W	0xFFFF.FFFF	Watchdog Load	778
0x004	WDTVALUE	RO	0xFFFF.FFFF	Watchdog Value	779
0x008	WDTCTL	R/W	0x0000.0000 (WDT0) 0x8000.0000 (WDT1)	Watchdog Control	780
0x00C	WDTICR	WO	-	Watchdog Interrupt Clear	782
0x010	WDTRIS	RO	0x0000.0000	Watchdog Raw Interrupt Status	783
0x014	WDTMIS	RO	0x0000.0000	Watchdog Masked Interrupt Status	784
0x418	WDTTEST	R/W	0x0000.0000	Watchdog Test	785
0xC00	WDTLOCK	R/W	0x0000.0000	Watchdog Lock	786
0xFD0	WDTPeriphID4	RO	0x0000.0000	Watchdog Peripheral Identification 4	787
0xFD4	WDTPeriphID5	RO	0x0000.0000	Watchdog Peripheral Identification 5	788
0xFD8	WDTPeriphID6	RO	0x0000.0000	Watchdog Peripheral Identification 6	789
0xFDC	WDTPeriphID7	RO	0x0000.0000	Watchdog Peripheral Identification 7	790
0xFE0	WDTPeriphID0	RO	0x0000.0005	Watchdog Peripheral Identification 0	791
0xFE4	WDTPeriphID1	RO	0x0000.0018	Watchdog Peripheral Identification 1	792
0xFE8	WDTPeriphID2	RO	0x0000.0018	Watchdog Peripheral Identification 2	793
0xFEC	WDTPeriphID3	RO	0x0000.0001	Watchdog Peripheral Identification 3	794
0xFF0	WDTPCellID0	RO	0x0000.000D	Watchdog PrimeCell Identification 0	795
0xFF4	WDTPCellID1	RO	0x0000.00F0	Watchdog PrimeCell Identification 1	796
0xFF8	WDTPCellID2	RO	0x0000.0006	Watchdog PrimeCell Identification 2	797
0xFFC	WDTPCellID3	RO	0x0000.00B1	Watchdog PrimeCell Identification 3	798

12.5 Register Descriptions

The remainder of this section lists and describes the WDT registers, in numerical order by address offset.

Register 1: Watchdog Load (WDTLOAD), offset 0x000


This register is the 32-bit interval value used by the 32-bit counter. When this register is written, the value is immediately loaded and the counter restarts counting down from the new value. If the **WDTLOAD** register is loaded with 0x0000.0000, an interrupt is immediately generated.

Watchdog Load (WDTLOAD)

WDT0 base: 0x4000.0000 WDT1 base: 0x4000.1000

Offset 0x000

Type R/W, reset 0xFFFF.FFFF



Bit/Field Name Type Reset Description

31:0 WDTLOAD R/W 0xFFF.FFFF Watchdog Load Value


Register 2: Watchdog Value (WDTVALUE), offset 0x004

This register contains the current count value of the timer.

Watchdog Value (WDTVALUE)

WDT0 base: 0x4000.0000 WDT1 base: 0x4000.1000 Offset 0x004

Type RO, reset 0xFFFF.FFFF



Bit/Field Name Type Reset Description

31:0 WDTVALUE RO 0xFFF.FFFF Watchdog Value

Current value of the 32-bit down counter.

Register 3: Watchdog Control (WDTCTL), offset 0x008

This register is the watchdog control register. The watchdog timer can be configured to generate a reset signal (on second time-out) or an interrupt on time-out.

When the watchdog interrupt has been enabled by setting the INTEN bit, all subsequent writes to the INTEN bit are ignored. The only mechanism that can re-enable writes to this bit is a hardware reset.

Important: Because the Watchdog Timer 1 module has an independent clocking domain, its registers must be written with a timing gap between accesses. Software must guarantee that this delay is inserted between back-to-back writes to WDT1 registers or between a write followed by a read to the registers. The timing for back-to-back reads from the WDT1 module has no restrictions. The WRC bit in the Watchdog Control (WDTCTL) register for WDT1 indicates that the required timing gap has elapsed. This bit is cleared on a write operation and set once the write completes, indicating to software that another write or read may be started safely. Software should poll WDTCTL for WRC=1 prior to accessing another register. Note that WDT0 does not have this restriction as it runs off the system clock and therefore does not have a WRC bit.

Watchdog Control (WDTCTL)


WDT0 base: 0x4000.0000 WDT1 base: 0x4000.1000

Offset 0x008

30:3

Type R/W, reset 0x0000.0000 (WDT0) and 0x8000.0000 (WDT1)

reserved



Bit/Field	Name	Type	Reset	Description
31	WRC	RO	1	Write Complete

RO

The WRC values are defined as follows:

Value Description

- 0 A write access to one of the WDT1 registers is in progress.
- A write access is not in progress, and WDT1 registers can be 1 read or written.

This bit is reserved for WDT0 and has a reset value of 0. Note:

0x000 000 Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be

preserved across a read-modify-write operation.

Bit/Field	Name	Туре	Reset	Description
2	INTTYPE	R/W	0	Watchdog Interrupt Type The INTTYPE values are defined as follows:
				Value Description
				0 Watchdog interrupt is a standard interrupt.
				1 Watchdog interrupt is a non-maskable interrupt.
1	RESEN	R/W	0	Watchdog Reset Enable
				The RESEN values are defined as follows:
				Value Description
				0 Disabled.
				1 Enable the Watchdog module reset output.
0	INTEN	R/W	0	Watchdog Interrupt Enable
				The INTEN values are defined as follows:
				Value Description
				0 Interrupt event disabled (once this bit is set, it can only be cleared by a hardware reset).
				1 Interrupt event enabled. Once enabled, all writes are ignored.


Register 4: Watchdog Interrupt Clear (WDTICR), offset 0x00C

This register is the interrupt clear register. A write of any value to this register clears the Watchdog interrupt and reloads the 32-bit counter from the WDTLOAD register. Value for a read or reset is indeterminate.

Watchdog Interrupt Clear (WDTICR)

WDT0 base: 0x4000.0000 WDT1 base: 0x4000.1000 Offset 0x00C

Type WO, reset -



Bit/Field Reset Description Name Type 31:0 **WDTINTCLR** WO Watchdog Interrupt Clear


Register 5: Watchdog Raw Interrupt Status (WDTRIS), offset 0x010

This register is the raw interrupt status register. Watchdog interrupt events can be monitored via this register if the controller interrupt is masked.

Watchdog Raw Interrupt Status (WDTRIS)

WDT0 base: 0x4000.0000 WDT1 base: 0x4000.1000 Offset 0x010

Type RO, reset 0x0000.0000



Bit/Field	Name	Type	Reset	Description
31:1	reserved	RO	0x0000.000	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
0	WDTRIS	RO	0	Watchdog Raw Interrupt Status

- A watchdog time-out event has occurred.
- 0 The watchdog has not timed out.


Register 6: Watchdog Masked Interrupt Status (WDTMIS), offset 0x014

This register is the masked interrupt status register. The value of this register is the logical AND of the raw interrupt bit and the Watchdog interrupt enable bit.

Watchdog Masked Interrupt Status (WDTMIS)

WDT0 base: 0x4000.0000 WDT1 base: 0x4000.1000 Offset 0x014

Type RO, reset 0x0000.0000



Bit/Field	Name	Type	Reset	Description
31:1	reserved	RO	0x0000.000	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
0	WDTMIS	RO	0	Watchdog Masked Interrupt Status

- A watchdog time-out event has been signalled to the interrupt controller.
- 0 The watchdog has not timed out or the watchdog timer interrupt is masked.

Register 7: Watchdog Test (WDTTEST), offset 0x418

This register provides user-enabled stalling when the microcontroller asserts the CPU halt flag during debug.

Watchdog Test (WDTTEST)

WDT0 base: 0x4000.0000 WDT1 base: 0x4000.1000


Offset 0x418

Bit/Field

Name

Type

Type R/W, reset 0x0000.0000



31:9	reserved	RO	0x0000.00	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
8	STALL	R/W	0	Watchdog Stall Enable

Description

Reset

- 1 If the microcontroller is stopped with a debugger, the watchdog timer stops counting. Once the microcontroller is restarted, the watchdog timer resumes counting.
- The watchdog timer continues counting if the microcontroller is stopped with a debugger.
- 7:0 reserved RO 0x00 Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.

Register 8: Watchdog Lock (WDTLOCK), offset 0xC00


Writing 0x1ACC.E551 to the WDTLOCK register enables write access to all other registers. Writing any other value to the WDTLOCK register re-enables the locked state for register writes to all the other registers. Reading the WDTLOCK register returns the lock status rather than the 32-bit value written. Therefore, when write accesses are disabled, reading the WDTLOCK register returns 0x0000.0001 (when locked; otherwise, the returned value is 0x0000.0000 (unlocked)).

Watchdog Lock (WDTLOCK)

WDT0 base: 0x4000.0000 WDT1 base: 0x4000.1000

Offset 0xC00

Type R/W, reset 0x0000.0000



A write of the value 0x1ACC.E551 unlocks the watchdog registers for write access. A write of any other value reapplies the lock, preventing any register updates.

A read of this register returns the following values:

Value Description 0x0000.0001 Locked 0x0000.0000 Unlocked

Watchdog Lock


Register 9: Watchdog Peripheral Identification 4 (WDTPeriphID4), offset 0xFD0

The WDTPeriphIDn registers are hard-coded and the fields within the register determine the reset value.

Watchdog Peripheral Identification 4 (WDTPeriphID4)

WDT0 base: 0x4000.0000 WDT1 base: 0x4000.1000 Offset 0xFD0

Type RO, reset 0x0000.0000




Bit/Field	Name	Type	Reset	Description
31:8	reserved	RO	0x0000.00	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
7:0	PID4	RO	0x00	WDT Peripheral ID Register [7:0]

Register 10: Watchdog Peripheral Identification 5 (WDTPeriphID5), offset 0xFD4

The **WDTPeriphIDn** registers are hard-coded and the fields within the register determine the reset value.

Watchdog Peripheral Identification 5 (WDTPeriphID5)

WDT0 base: 0x4000.0000 WDT1 base: 0x4000.1000 Offset 0xFD4 Type RO, reset 0x0000.0000




Bit/Field	Name	Type	Reset	Description
31:8	reserved	RO	0x0000.00	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
7:0	PID5	RO	0x00	WDT Peripheral ID Register [15:8]

Register 11: Watchdog Peripheral Identification 6 (WDTPeriphID6), offset 0xFD8

The **WDTPeriphIDn** registers are hard-coded and the fields within the register determine the reset value.

Watchdog Peripheral Identification 6 (WDTPeriphID6)

WDT0 base: 0x4000.0000 WDT1 base: 0x4000.1000 Offset 0xFD8 Type RO, reset 0x0000.0000




Bit/Field	Name	Type	Reset	Description
31:8	reserved	RO	0x0000.00	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
7:0	PID6	RO	0x00	WDT Peripheral ID Register [23:16]

Register 12: Watchdog Peripheral Identification 7 (WDTPeriphID7), offset 0xFDC

The **WDTPeriphIDn** registers are hard-coded and the fields within the register determine the reset value.

Watchdog Peripheral Identification 7 (WDTPeriphID7)

WDT0 base: 0x4000.0000 WDT1 base: 0x4000.1000 Offset 0xFDC Type RO, reset 0x0000.0000




Bit/Field	Name	Type	Reset	Description
31:8	reserved	RO	0x0000.00	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
7:0	PID7	RO	0x00	WDT Peripheral ID Register [31:24]

Register 13: Watchdog Peripheral Identification 0 (WDTPeriphID0), offset 0xFE0

The **WDTPeriphIDn** registers are hard-coded and the fields within the register determine the reset value.

Watchdog Peripheral Identification 0 (WDTPeriphID0)

WDT0 base: 0x4000.0000 WDT1 base: 0x4000.1000 Offset 0xFE0 Type RO, reset 0x0000.0005




Bit/Field	Name	Type	Reset	Description
31:8	reserved	RO	0x0000.00	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
7:0	PID0	RO	0x05	Watchdog Peripheral ID Register [7:0]

Register 14: Watchdog Peripheral Identification 1 (WDTPeriphID1), offset 0xFE4

The **WDTPeriphIDn** registers are hard-coded and the fields within the register determine the reset value.

Watchdog Peripheral Identification 1 (WDTPeriphID1)

WDT0 base: 0x4000.0000 WDT1 base: 0x4000.1000 Offset 0xFE4 Type RO, reset 0x0000.0018




Bit/Field	Name	Type	Reset	Description
31:8	reserved	RO	0x0000.00	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
7:0	PID1	RO	0x18	Watchdog Peripheral ID Register [15:8]

Register 15: Watchdog Peripheral Identification 2 (WDTPeriphID2), offset 0xFE8

The **WDTPeriphIDn** registers are hard-coded and the fields within the register determine the reset value.

Watchdog Peripheral Identification 2 (WDTPeriphID2)

WDT0 base: 0x4000.0000 WDT1 base: 0x4000.1000 Offset 0xFE8 Type RO, reset 0x0000.0018




Bit/Field	Name	Туре	Reset	Description
31:8	reserved	RO	0x0000.00	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
7:0	PID2	RO	0x18	Watchdog Peripheral ID Register [23:16]

Register 16: Watchdog Peripheral Identification 3 (WDTPeriphID3), offset 0xFEC

The **WDTPeriphIDn** registers are hard-coded and the fields within the register determine the reset value.

Watchdog Peripheral Identification 3 (WDTPeriphID3)

WDT0 base: 0x4000.0000 WDT1 base: 0x4000.1000 Offset 0xFEC Type RO, reset 0x0000.0001



Bit/Field	Name	Type	Reset	Description
31:8	reserved	RO	0x0000.00	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
7:0	PID3	RO	0x01	Watchdog Peripheral ID Register [31:24]


Register 17: Watchdog PrimeCell Identification 0 (WDTPCellID0), offset 0xFF0

The WDTPCellIDn registers are hard-coded and the fields within the register determine the reset value.

Watchdog PrimeCell Identification 0 (WDTPCellID0)

WDT0 base: 0x4000.0000 WDT1 base: 0x4000.1000 Offset 0xFF0

Type RO, reset 0x0000.000D



Bit/Field	Name	Type	Reset	Description
31:8	reserved	RO	0x0000.00	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
7:0	CID0	RO	0x0D	Watchdog PrimeCell ID Register [7:0]


Register 18: Watchdog PrimeCell Identification 1 (WDTPCellID1), offset 0xFF4

The WDTPCellIDn registers are hard-coded and the fields within the register determine the reset value.

Watchdog PrimeCell Identification 1 (WDTPCellID1)

WDT0 base: 0x4000.0000 WDT1 base: 0x4000.1000 Offset 0xFF4

Type RO, reset 0x0000.00F0



Bit/Field	Name	Туре	Reset	Description
31:8	reserved	RO	0x0000.00	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
7:0	CID1	RO	0xF0	Watchdog PrimeCell ID Register [15:8]


Register 19: Watchdog PrimeCell Identification 2 (WDTPCellID2), offset 0xFF8

The WDTPCellIDn registers are hard-coded and the fields within the register determine the reset value.

Watchdog PrimeCell Identification 2 (WDTPCellID2)

WDT0 base: 0x4000.0000 WDT1 base: 0x4000.1000 Offset 0xFF8

Type RO, reset 0x0000.0006



Bit/Field	Name	Type	Reset	Description
31:8	reserved	RO	0x0000.00	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
7:0	CID2	RO	0x06	Watchdog PrimeCell ID Register [23:16]


Register 20: Watchdog PrimeCell Identification 3 (WDTPCellID3), offset 0xFFC

The WDTPCellIDn registers are hard-coded and the fields within the register determine the reset value.

Watchdog PrimeCell Identification 3 (WDTPCellID3)

WDT0 base: 0x4000.0000 WDT1 base: 0x4000.1000 Offset 0xFFC

Type RO, reset 0x0000.00B1



Bit/Field	Name	Type	Reset	Description
31:8	reserved	RO	0x0000.00	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
7:0	CID3	RO	0xB1	Watchdog PrimeCell ID Register [31:24]

13 Analog-to-Digital Converter (ADC)

An analog-to-digital converter (ADC) is a peripheral that converts a continuous analog voltage to a discrete digital number. Two identical converter modules are included, which share 22 input channels.

The Stellaris[®] ADC module features 12-bit conversion resolution and supports 22 input channels, plus an internal temperature sensor. Each ADC module contains four programmable sequencers allowing the sampling of multiple analog input sources without controller intervention. Each sample sequencer provides flexible programming with fully configurable input source, trigger events, interrupt generation, and sequencer priority. A digital comparator function is included which allows the conversion value to be diverted to a digital comparator module. Each ADC module provides eight digital comparators. Each digital comparator evaluates the ADC conversion value against its two user-defined values to determine the operational range of the signal. The trigger source for ADC0 and ADC1 may be independent or the two ADC modules may operate from the same trigger source and operate on the same or different inputs. A phase shifter can delay the start of sampling by a specified phase angle. When using both ADC modules, it is possible to configure the converters to start the conversions coincidentally or within a relative phase from each other, see "Sample Phase Control" on page 805.

The Stellaris LM4F232H5QC microcontroller provides two ADC modules with each having the following features:

- 22 shared analog input channels
- 12-bit precision ADC
- Single-ended and differential-input configurations
- On-chip internal temperature sensor
- Maximum sample rate of one million samples/second
- Optional phase shift in sample time programmable from 22.5° to 337.5°
- Four programmable sample conversion sequencers from one to eight entries long, with corresponding conversion result FIFOs
- Flexible trigger control
 - Controller (software)
 - Timers
 - Analog Comparators
 - PWM
 - GPIO
- Hardware averaging of up to 64 samples
- Digital comparison unit providing eight digital comparators
- Converter uses two external reference signals or VDDA and GNDA as the voltage reference

- Power and ground for the analog circuitry is separate from the digital power and ground
- Efficient transfers using Micro Direct Memory Access Controller (μDMA)
 - Dedicated channel for each sample sequencer
 - ADC module uses burst requests for DMA

13.1 Block Diagram

The Stellaris microcontroller contains two identical Analog-to-Digital Converter modules. These two modules, ADC0 and ADC1, share the same 22 analog input channels. Each ADC module operates independently and can therefore execute different sample sequences, sample any of the analog input channels at any time, and generate different interrupts and triggers. Figure 13-1 on page 800 shows how the two modules are connected to analog inputs and the system bus.

Figure 13-1. Implementation of Two ADC Blocks




Figure 13-2 on page 801 provides details on the internal configuration of the ADC controls and data registers.




Figure 13-2. ADC Module Block Diagram

13.2 Signal Description

The following table lists the external signals of the ADC module and describes the function of each. The AINx signals are analog functions for some GPIO signals. The column in the table below titled "Pin Mux/Pin Assignment" lists the GPIO pin placement for the ADC signals. These signals are configured by clearing the corresponding DEN bit in the GPIO Digital Enable (GPIODEN) register and setting the corresponding AMSEL bit in the GPIO Analog Mode Select (GPIOAMSEL) register. For more information on configuring GPIOs, see "General-Purpose Input/Outputs (GPIOs)" on page 646. The VREFA+ and VREFA- signals (with the word "fixed" in the Pin Mux/Pin Assignment column) have a fixed pin assignment and function and are not 5-V tolerant.

Table 13-1. ADC Signals (100LQFP)

Pin Name	Pin Number	Pin Mux / Pin Assignment	Pin Type	Buffer Type ^a	Description
AIN0	12	PE3	1	Analog	Analog-to-digital converter input 0.
AIN1	13	PE2	1	Analog	Analog-to-digital converter input 1.
AIN2	14	PE1	1	Analog	Analog-to-digital converter input 2.
AIN3	15	PE0	I	Analog	Analog-to-digital converter input 3.
AIN4	100	PD7	1	Analog	Analog-to-digital converter input 4.
AIN5	99	PD6	1	Analog	Analog-to-digital converter input 5.
AIN6	98	PD5	I	Analog	Analog-to-digital converter input 6.
AIN7	97	PD4	Ţ	Analog	Analog-to-digital converter input 7.

Table 13-1. ADC Signals (100LQFP) (continued)

Pin Name	Pin Number	Pin Mux / Pin Assignment	Pin Type	Buffer Type ^a	Description
AIN8	96	PE5	I	Analog	Analog-to-digital converter input 8.
AIN9	95	PE4	I	Analog	Analog-to-digital converter input 9.
AIN10	92	PB4	ļ	Analog	Analog-to-digital converter input 10.
AIN11	91	PB5	ļ	Analog	Analog-to-digital converter input 11.
AIN12	4	PD3	I	Analog	Analog-to-digital converter input 12.
AIN13	3	PD2	ļ	Analog	Analog-to-digital converter input 13.
AIN14	2	PD1	ļ	Analog	Analog-to-digital converter input 14.
AIN15	1	PD0	ļ	Analog	Analog-to-digital converter input 15.
AIN16	16	PH0	ļ	Analog	Analog-to-digital converter input 16.
AIN17	17	PH1	ļ	Analog	Analog-to-digital converter input 17.
AIN18	18	PH2	ļ	Analog	Analog-to-digital converter input 18.
AIN19	19	PH3	ļ	Analog	Analog-to-digital converter input 19.
AIN20	90	PE7	I	Analog	Analog-to-digital converter input 20.
AIN21	89	PE6	ļ	Analog	Analog-to-digital converter input 21.
VREFA+	8	fixed	-	Analog	A reference voltage used to specify the voltage at which the ADC converts to a maximum value. This pin is used in conjunction with VREFA- which specifies the minimum value. In other words, the voltage that is applied to VREFA+ is the voltage with which an AINn signal is converted to 4095. The VREFA+ voltage is limited to the range specified in Table 24-31 on page 1403.
VREFA-	9	fixed	-	Analog	A reference voltage used to specify the input voltage at which the ADC converts to a minimum value. This pin is used in conjunction with VREFA+ which specifies the maximum value. In other words, the voltage that is applied to VREFA- is the voltage with which an AINn signal is converted to 0, while the voltage that is applied to VREFA+ is the voltage with which an AINn signal is converted to 4095. The VREFA- voltage is limited to the range specified in Table 24-31 on page 1403.

a. The TTL designation indicates the pin has TTL-compatible voltage levels.

13.3 Functional Description

The Stellaris ADC collects sample data by using a programmable sequence-based approach instead of the traditional single or double-sampling approaches found on many ADC modules. Each *sample sequence* is a fully programmed series of consecutive (back-to-back) samples, allowing the ADC to collect data from multiple input sources without having to be re-configured or serviced by the processor. The programming of each sample in the sample sequence includes parameters such as the input source and mode (differential versus single-ended input), interrupt generation on sample completion, and the indicator for the last sample in the sequence. In addition, the μ DMA can be used to more efficiently move data from the sample sequencers without CPU intervention.

13.3.1 Sample Sequencers

The sampling control and data capture is handled by the sample sequencers. All of the sequencers are identical in implementation except for the number of samples that can be captured and the depth

of the FIFO. Table 13-2 on page 803 shows the maximum number of samples that each sequencer can capture and its corresponding FIFO depth. Each sample that is captured is stored in the FIFO. In this implementation, each FIFO entry is a 32-bit word, with the lower 12 bits containing the conversion result.

Table 13-2. Samples and FIFO Depth of Sequencers

Sequencer	Number of Samples	Depth of FIFO
SS3	1	1
SS2	4	4
SS1	4	4
SS0	8	8

For a given sample sequence, each sample is defined by bit fields in the ADC Sample Sequence Input Multiplexer Select (ADCSSMUXn), ADC Sample Sequence Extended Input Multiplexer Select (ADCSSEMUXn) and ADC Sample Sequence Control (ADCSSCTLn) registers, where "n" corresponds to the sequence number. The ADCSSMUXn and ADCSSEMUXn fields select the input pin, while the ADCSSCTLn fields contain the sample control bits corresponding to parameters such as temperature sensor selection, interrupt enable, end of sequence, and differential input mode. Sample sequencers are enabled by setting the respective ASENn bit in the ADC Active Sample Sequencer (ADCACTSS) register and should be configured before being enabled. Sampling is then initiated by setting the SSn bit in the ADC Processor Sample Sequence Initiate (ADCPSSI) register. In addition, sample sequences may be initiated on multiple ADC modules simultaneously using the GSYNC and SYNCWAIT bits in the ADCPSSI register during the configuration of each ADC module. For more information on using these bits, refer to page 845.

When configuring a sample sequence, multiple uses of the same input pin within the same sequence are allowed. In the **ADCSSCTLn** register, the <code>len</code> bits can be set for any combination of samples, allowing interrupts to be generated after every sample in the sequence if necessary. Also, the <code>END</code> bit can be set at any point within a sample sequence. For example, if Sequencer 0 is used, the <code>END</code> bit can be set in the nibble associated with the fifth sample, allowing Sequencer 0 to complete execution of the sample sequence after the fifth sample.

After a sample sequence completes execution, the result data can be retrieved from the **ADC Sample Sequence Result FIFO** (**ADCSSFIFOn**) registers. The FIFOs are simple circular buffers that read a single address to "pop" result data. For software debug purposes, the positions of the FIFO head and tail pointers are visible in the **ADC Sample Sequence FIFO Status (ADCSSFSTATn)** registers along with FULL and EMPTY status flags. If a write is attempted when the FIFO is full, the write does not occur and an overflow condition is indicated. Overflow and underflow conditions are monitored using the **ADCOSTAT** and **ADCUSTAT** registers.

13.3.2 Module Control

Outside of the sample sequencers, the remainder of the control logic is responsible for tasks such as:

- Interrupt generation
- DMA operation
- Sequence prioritization
- Trigger configuration

- Comparator configuration
- External voltage reference
- Sample phase control
- Module clocking

Most of the ADC control logic runs at the ADC clock rate of 16 MHz. The internal ADC divider is configured for 16-MHz operation automatically by hardware when the system XTAL is selected with the PLL.

13.3.2.1 Interrupts

The register configurations of the sample sequencers and digital comparators dictate which events generate raw interrupts, but do not have control over whether the interrupt is actually sent to the interrupt controller. The ADC module's interrupt signals are controlled by the state of the MASK bits in the ADC Interrupt Mask (ADCIM) register. Interrupt status can be viewed at two locations: the ADC Raw Interrupt Status (ADCRIS) register, which shows the raw status of the various interrupt signals; and the ADC Interrupt Status and Clear (ADCISC) register, which shows active interrupts that are enabled by the ADCIM register. Sequencer interrupts are cleared by writing a 1 to the corresponding IN bit in ADCISC. Digital comparator interrupts are cleared by writing a 1 to the ADC Digital Comparator Interrupt Status and Clear (ADCDCISC) register.

13.3.2.2 DMA Operation

DMA may be used to increase efficiency by allowing each sample sequencer to operate independently and transfer data without processor intervention or reconfiguration. The ADC module provides a request signal from each sample sequencer to the associated dedicated channel of the μ DMA controller. The ADC does not support single transfer requests. A burst transfer request is asserted when the interrupt bit for the sample sequence is set (IE bit in the **ADCSSCTLn** register is set).

The arbitration size of the μ DMA transfer must be a power of 2, and the associated IE bits in the **ADCSSCTLn** register must be set. For example, if the μ DMA channel of SS0 has an arbitration size of four, the IE3 bit (4th sample) and the IE7 bit (8th sample) must be set. Thus the μ DMA request occurs every time 4 samples have been acquired. No other special steps are needed to enable the ADC module for μ DMA operation.

Refer to the "Micro Direct Memory Access (μ DMA)" on page 582 for more details about programming the μ DMA controller.

13.3.2.3 Prioritization

When sampling events (triggers) happen concurrently, they are prioritized for processing by the values in the **ADC Sample Sequencer Priority (ADCSSPRI)** register. Valid priority values are in the range of 0-3, with 0 being the highest priority and 3 being the lowest. Multiple active sample sequencer units with the same priority do not provide consistent results, so software must ensure that all active sample sequencer units have a unique priority value.

13.3.2.4 Sampling Events


Sample triggering for each sample sequencer is defined in the **ADC Event Multiplexer Select (ADCEMUX)** register. Trigger sources include processor (default), analog comparators, an external signal on a GPIO specified by the **GPIO ADC Control (GPIOADCCTL)** register, a GP Timer, a PWM generator, and continuous sampling. The processor triggers sampling by setting the SSx bits in the **ADC Processor Sample Sequence Initiate (ADCPSSI)** register.

Care must be taken when using the continuous sampling trigger. If a sequencer's priority is too high, it is possible to starve other lower priority sequencers. Generally, a sample sequencer using continuous sampling should be set to the lowest priority. Continuous sampling can be used with a digital comparator to cause an interrupt when a particular voltage is seen on an input.

13.3.2.5 Sample Phase Control


The trigger source for ADC0 and ADC1 may be independent or the two ADC modules may operate from the same trigger source and operate on the same or different inputs. If the converters are running at the same sample rate, they may be configured to start the conversions coincidentally or with one of 15 different discrete phases relative to each other. The sample time can be delayed from the standard sampling time in 22.5° increments up to 337.5° using the **ADC Sample Phase Control (ADCSPC)** register. Figure 13-3 on page 805 shows an example of various phase relationships at a 1 Msps rate.

Figure 13-3. ADC Sample Phases



This feature can be used to double the sampling rate of an input. Both ADC module 0 and ADC module 1 can be programmed to sample the same input. ADC module 0 could sample at the standard position (the PHASE field in the ADCSPC register is 0x0). ADC module 1 can be configured to sample at 180 (PHASE = 0x8). The two modules can be be synchronized using the GSYNC and SYNCWAIT bits in the ADC Processor Sample Sequence Initiate (ADCPSSI) register. Software could then combine the results from the two modules to create a sample rate of two million samples/second at 16 MHz as shown in Figure 13-4 on page 805.

Figure 13-4. Doubling the ADC Sample Rate




Using the **ADCSPC** register, ADC0 and ADC1 may provide a number of interesting applications:

- Coincident sampling of different signals. The sample sequence steps run coincidently in both converters.
 - ADC Module 0, ADCSPC = 0x0, sampling AIN0
 - ADC Module 1, ADCSPC = 0x0, sampling AIN1

- Skewed sampling of the same signal. The sample sequence steps are 1/2 of an ADC clock (500 μs for a 1Ms/s ADC) out of phase with each other. This configuration doubles the conversion bandwidth of a single input when software combines the results as shown in Figure 13-5 on page 806.
 - ADC Module 0, ADCSPC = 0x0, sampling AIN0
 - ADC Module 1, ADCSPC = 0x8, sampling AIN0

Figure 13-5. Skewed Sampling



13.3.2.6 Module Clocking

The module is clocked by a 16-MHz clock which can be sourced by a divided version of the PLL output, the PIOSC or an external source connected to MOSC (with the PLL in bypass mode). When the PLL is operating, the ADC clock is derived from the PLL ÷ 25 by default. However, the PIOSC can be used for the module clock using the **ADC Clock Configuration (ADCCC)** register. To use the PIOSC to clock the ADC, first power up the PLL and then enable the PIOSC in the CS bit field in the **ADCCC** register, then disable the PLL. When the PLL is bypassed, the module clock source clock attached to the MOSC must be 16 MHz unless the PIOSC is used for the clock source. To use the MOSC to clock the ADC, first power up the PLL and then enable the clock to the ADC module, then disable the PLL and switch to the MOSC for the system clock. The ADC module can continue to operate in Deep-Sleep mode if the PIOSC is the ADC module clock source.

The system clock must be at the same frequency or higher than the ADC clock. All ADC modules share the same clock source to facilitate the synchronization of data samples between conversion units, the selection and programming of which is provided by ADC0's **ADCCC** register. The ADC modules do not run at different conversion rates.

13.3.2.7 Busy Status

The BUSY bit of the **ADCACTSS** register is used to indicate when the ADC is busy with a current conversion. When there are no triggers pending which may start a new conversion in the immediate cycle or next few cycles, the BUSY bit reads as 0. Software must read the status of the BUSY bit as clear before disabling the ADC clock by writing to the **Analog-to-Digital Converter Run Mode Clock Gating Control (RCGCADC)** register.

13.3.2.8 Dither Enable

The **ADCCTL** register provides a dither enable bit to reduce random noise in ADC sampling. The DITHER bit is disabled by default at reset. For dither accuracy, please refer to "Electrical Characteristics" on page 1376.


13.3.3 Hardware Sample Averaging Circuit

Higher precision results can be generated using the hardware averaging circuit, however, the improved results are at the cost of throughput. Up to 64 samples can be accumulated and averaged to form a single data entry in the sequencer FIFO. Throughput is decreased proportionally to the number of samples in the averaging calculation. For example, if the averaging circuit is configured to average 16 samples, the throughput is decreased by a factor of 16.

By default the averaging circuit is off, and all data from the converter passes through to the sequencer FIFO. The averaging hardware is controlled by the **ADC Sample Averaging Control (ADCSAC)** register (see page 847). A single averaging circuit has been implemented, thus all input channels receive the same amount of averaging whether they are single-ended or differential.

Figure 13-6 shows an example in which the **ADCSAC** register is set to 0x2 for 4x hardware oversampling and the IE1 bit is set for the sample sequence, resulting in an interrupt after the second averaged value is stored in the FIFO.

Figure 13-6. Sample Averaging Example




13.3.4 Analog-to-Digital Converter

The Analog-to-Digital Converter (ADC) module uses a Successive Approximation Register (SAR) architecture to deliver a 12-bit, low-power, high-precision conversion value. The successive approximation uses a switched capacitor array to perform the dual functions of sampling and holding the signal as well as providing the 12-bit DAC operation. The ADC requires a 16-MHz clock. This clock can be a divided version of the PLL output, the PIOSC or a 16-MHz clock source connected to MOSC. The MOSC provides the best results, followed by the PLL divided down, and then the

PIOSC. Figure 13-7 shows the ADC input equivalency diagram; for parameter values, see "Analog-to-Digital Converter (ADC)" on page 1403.

Figure 13-7. ADC Input Equivalency Diagram




The ADC operates from both the 3.3-V analog and 1.2-V digital power supplies. The ADC clock can be configured to reduce power consumption when ADC conversions are not required (see "System Control" on page 231). The analog inputs are connected to the ADC through specially balanced input paths to minimize the distortion and cross-talk on the inputs. Detailed information on the ADC power supplies and analog inputs can be found in "Analog-to-Digital Converter (ADC)" on page 1403.

13.3.4.1 Voltage Reference

The ADC uses internal signals VREFP and VREFN as references to produce a conversion value from the selected analog input. VREFP can be connected to either VREFA+ or VDDA and VREFN can be connected to either VREFA- or GNDA as configured by the VREF bit in the **ADC Control** (**ADCCTL**) register, as shown in Figure 13-8.

Figure 13-8. ADC Voltage Reference



The range of this conversion value is from 0x000 to 0xFFF. In single-ended-input mode, the 0x000 value corresponds to the voltage level on VREFN; the 0xFFF value corresponds to the voltage level on VREFP. This configuration results in a resolution that can be calculated using the following equation:

```
mV per ADC code = (VREFP - VREFN) / 4096
```

While the analog input pads can handle voltages beyond this range, the ADC conversions saturate in under-voltage and over-voltage cases. Analog input voltages above VREFP saturate at 0xFFF while those below VREFN saturate at 0x000. The V_{REF+} and V_{REF-} specifications define the useful range for the external voltage references on VDDA+ and VDDA-, see Table 24-31 on page 1403. Care must be taken to supply a reference voltage of acceptable quality. Figure 13-9 on page 810 shows the ADC conversion function of the analog inputs.

February 20, 2013 809




Figure 13-9. ADC Conversion Result

13.3.5 Differential Sampling

In addition to traditional single-ended sampling, the ADC module supports differential sampling of two analog input channels. To enable differential sampling, software must set the \mathtt{Dn} bit in the **ADCSSCTL0n** register in a step's configuration nibble.

When a sequence step is configured for differential sampling, the input pair to sample must be configured in the **ADCSSMUXn** register. Differential pair 0 samples analog inputs 0 and 1; differential pair 1 samples analog inputs 2 and 3; and so on (see Table 13-3 on page 810). The ADC does not support other differential pairings such as analog input 0 with analog input 3.

Table 13-3. Differential Sampling Pairs

Differential Pair	Analog Inputs
0	0 and 1
1	2 and 3
2	4 and 5
3	6 and 7
4	8 and 9
5	10 and 11
6	12 and 13

Table 13-3. Differential Sampling Pairs (continued)

Differential Pair	Analog Inputs
7	14 and 15
8	16 and 17
9	18 and 19
10	20 and 21

The voltage sampled in differential mode is the difference between the odd and even channels:

- Input Positive Voltage: VIN+ = V_{IN EVEN} (even channel)
- Input Negative Voltage: VIN- = V_{IN ODD} (odd channel)

The input differential voltage is defined as: $VIN_D = VIN+ - VIN-$, therefore:

- If $VIN_D = 0$, then the conversion result = 0x800
- If $VIN_D > 0$, then the conversion result > 0x800 (range is 0x800–0xFFF)
- If $VIN_D < 0$, then the conversion result < 0x800 (range is 0–0x800)

When using differential sampling, the following definitions are relevant:

- Input Common Mode Voltage: VIN_{CM} = (VIN+ + VIN-) / 2
- Reference Positive Voltage: VREFP
- Reference Negative Voltage: VREFN
- Reference Differential Voltage: VREF_D = VREFP VREFN
- Reference Common Mode Voltage: VREF_{CM} = (VREFP + VREFN) / 2

The following conditions provide optimal results in differential mode:

- Both V_{IN_EVEN} and V_{IN_ODD} must be in the range of (VREFP to VREFN) for a valid conversion result
- The maximum possible differential input swing, or the maximum differential range, is: -VREF_Dto +VREF_D, so the maximum peak-to-peak input differential signal is (+VREF_D -VREF_D) = 2 * VREF_D = 2 * (VREFP VREFN)
- In order to take advantage of the maximum possible differential input swing, VIN_{CM} should be very close to VREF_{CM}, see Table 24-31 on page 1403.

If VIN_{CM} is not equal to $VREF_{CM}$, the differential input signal may clip at either maximum or minimum voltage, because either single ended input can never be larger than VREFP or smaller than VREFN, and it is not possible to achieve full swing. Thus any difference in common mode between the input voltage and the reference voltage limits the differential dynamic range of the ADC.

Because the maximum peak-to-peak differential signal voltage is 2 * (VREFP - VREFN), the ADC codes are interpreted as:

```
mV per ADC code = (2 *(VREFP - VREFN)) / 4096
```

Figure 13-10 shows how the differential voltage, ΔV , is represented in ADC codes.





Figure 13-10. Differential Voltage Representation



13.3.6 **Internal Temperature Sensor**

The temperature sensor serves two primary purposes: 1) to notify the system that internal temperature is too high or low for reliable operation and 2) to provide temperature measurements for calibration of the Hibernate module RTC trim value.

The temperature sensor does not have a separate enable, because it also contains the bandgap reference and must always be enabled. The reference is supplied to other analog modules; not just the ADC. In addition, the temperature sensor has a second power-down input in the 3.3 V domain which provides control by the Hibernation module.

The internal temperature sensor converts a temperature measurement into a voltage. This voltage value, V_{TSENS}, is given by the following equation (where TEMP is the temperature in °C):

$$V_{TSENS} = 2.7 - ((TEMP + 55) / 75)$$

This relation is shown in Figure 13-11 on page 813.




Figure 13-11. Internal Temperature Sensor Characteristic

The temperature sensor reading can be sampled in a sample sequence by setting the ${\tt TSn}$ bit in the **ADCSSCTLn** register. The temperature reading from the temperature sensor can also be given as a function of the ADC value. The following formula calculates temperature (TEMP in °C) based on the ADC reading (ADC_{CODE}, given as an unsigned decimal number from 0 to 4095) and the maximum ADC voltage range (VREFP - VREFN):

TEMP =
$$147.5 - ((75 * (VREFP - VREFN) \times ADC_{CODE}) / 4096)$$

13.3.7 Digital Comparator Unit

An ADC is commonly used to sample an external signal and to monitor its value to ensure that it remains in a given range. To automate this monitoring procedure and reduce the amount of processor overhead that is required, each module provides eight digital comparators.

Conversions from the ADC that are sent to the digital comparators are compared against the user programmable limits in the **ADC Digital Comparator Range (ADCDCCMPn)** registers. The ADC can be configured to generate an interrupt depending on whether the ADC is operating within the low, mid or high-band region configured in the ADCDCCMPn bit fields. The digital comparators four operational modes (Once, Always, Hysteresis Once, Hysteresis Always) can be additionally applied to the interrupt configuration.

13.3.7.1 Output Functions

ADC conversions can either be stored in the ADC Sample Sequence FIFOs or compared using the digital comparator resources as defined by the SnDCOP bits in the **ADC Sample Sequence n**Operation (ADCSSOPn) register. These selected ADC conversions are used by their respective

digital comparator to monitor the external signal. Each comparator has two possible output functions: processor interrupts and triggers.

Each function has its own state machine to track the monitored signal. Even though the interrupt and trigger functions can be enabled individually or both at the same time, the same conversion data is used by each function to determine if the right conditions have been met to assert the associated output.

Interrupts

The digital comparator interrupt function is enabled by setting the CIE bit in the **ADC Digital Comparator Control (ADCDCCTLn)** register. This bit enables the interrupt function state machine to start monitoring the incoming ADC conversions. When the appropriate set of conditions is met, and the DCONSSX bit is set in the **ADCIM** register, an interrupt is sent to the interrupt controller.

Note: Only a single DCONSSn bit should be set at any given time. Setting more than one of these bits results in the INRDC bit from the **ADCRIS** register being masked, and no interrupt is generated on any of the sample sequencer interrupt lines. It is recommended that when interrupts are used, they are enabled on alternating samples or at the end of the sample sequence.

Triggers

The digital comparator trigger function is enabled by setting the CTE bit in the **ADCDCCTLn** register. This bit enables the trigger function state machine to start monitoring the incoming ADC conversions. When the appropriate set of conditions is met, the corresponding digital comparator trigger to the PWM module is asserted

13.3.7.2 Operational Modes

Four operational modes are provided to support a broad range of applications and multiple possible signaling requirements: Always, Once, Hysteresis Always, and Hysteresis Once. The operational mode is selected using the CIM or CTM field in the **ADCDCCTLn** register.

Always Mode

In the Always operational mode, the associated interrupt or trigger is asserted whenever the ADC conversion value meets its comparison criteria. The result is a string of assertions on the interrupt or trigger while the conversions are within the appropriate range.

Once Mode

In the Once operational mode, the associated interrupt or trigger is asserted whenever the ADC conversion value meets its comparison criteria, and the previous ADC conversion value did not. The result is a single assertion of the interrupt or trigger when the conversions are within the appropriate range.

Hysteresis-Always Mode

The Hysteresis-Always operational mode can only be used in conjunction with the low-band or high-band regions because the mid-band region must be crossed and the opposite region entered to clear the hysteresis condition. In the Hysteresis-Always mode, the associated interrupt or trigger is asserted in the following cases: 1) the ADC conversion value meets its comparison criteria or 2) a previous ADC conversion value has met the comparison criteria, and the hysteresis condition has not been cleared by entering the opposite region. The result is a string of assertions on the interrupt or trigger that continue until the opposite region is entered.

Hysteresis-Once Mode

The Hysteresis-Once operational mode can only be used in conjunction with the low-band or high-band regions because the mid-band region must be crossed and the opposite region entered to clear the hysteresis condition. In the Hysteresis-Once mode, the associated interrupt or trigger is asserted only when the ADC conversion value meets its comparison criteria, the hysteresis condition is clear, and the previous ADC conversion did not meet the comparison criteria. The result is a single assertion on the interrupt or trigger.


13.3.7.3 Function Ranges

The two comparison values, COMPO and COMP1, in the ADC Digital Comparator Range (ADCDCCMPn) register effectively break the conversion area into three distinct regions. These regions are referred to as the low-band (less than COMPO), mid-band (greater than COMPO but less than or equal to COMP1), and high-band (greater than or equal to COMP1) regions. COMPO and COMP1 may be programmed to the same value, effectively creating two regions, but COMP1 must always be greater than or equal to the value of COMPO. A COMP1 value that is less than COMPO generates unpredictable results.

Low-Band Operation

To operate in the low-band region, the CIC field or the CTC field in the **ADCDCCTLn** register must be programmed to 0x0. This setting causes interrupts or triggers to be generated in the low-band region as defined by the programmed operational mode. An example of the state of the interrupt/trigger signal in the low-band region for each of the operational modes is shown in Figure 13-12 on page 815. Note that a "0" in a column following the operational mode name (Always, Once, Hysteresis Always, and Hysteresis Once) indicates that the interrupt or trigger signal is de-asserted and a "1" indicates that the signal is asserted.





Mid-Band Operation

To operate in the mid-band region, the CIC field or the CTC field in the **ADCDCCTLn** register must be programmed to 0x1. This setting causes interrupts or triggers to be generated in the mid-band region according the operation mode. Only the Always and Once operational modes are available in the mid-band region. An example of the state of the interrupt/trigger signal in the mid-band region for each of the allowed operational modes is shown in Figure 13-13 on page 816. Note that a "0" in a column following the operational mode name (Always or Once) indicates that the interrupt or trigger signal is de-asserted and a "1" indicates that the signal is asserted.




Figure 13-13. Mid-Band Operation (CIC=0x1 and/or CTC=0x1)

High-Band Operation

To operate in the high-band region, the CIC field or the CTC field in the **ADCDCCTLn** register must be programmed to 0x3. This setting causes interrupts or triggers to be generated in the high-band region according the operation mode. An example of the state of the interrupt/trigger signal in the high-band region for each of the allowed operational modes is shown in Figure 13-14 on page 817. Note that a "0" in a column following the operational mode name (Always, Once, Hysteresis Always, and Hysteresis Once) indicates that the interrupt or trigger signal is de-asserted and a "1" indicates that the signal is asserted.




Figure 13-14. High-Band Operation (CIC=0x3 and/or CTC=0x3)

13.4 Initialization and Configuration

In order for the ADC module to be used, the PLL must be enabled and programmed to a supported crystal frequency in the **RCC** register (see page 255). Using unsupported frequencies can cause faulty operation in the ADC module.

13.4.1 Module Initialization

Initialization of the ADC module is a simple process with very few steps: enabling the clock to the ADC, disabling the analog isolation circuit associated with all inputs that are to be used, and reconfiguring the sample sequencer priorities (if needed).

The initialization sequence for the ADC is as follows:

- 1. Enable the ADC clock using the RCGCADC register (see page 343).
- **2.** Enable the clock to the appropriate GPIO modules via the **RCGCGPIO** register (see page 330). To find out which GPIO ports to enable, refer to "Signal Description" on page 801.
- 3. Set the GPIO AFSEL bits for the ADC input pins (see page 670). To determine which GPIOs to configure, see Table 23-4 on page 1358.
- **4.** Configure the AINx signals to be analog inputs by clearing the corresponding DEN bit in the **GPIO Digital Enable (GPIODEN)** register (see page 681).
- **5.** Disable the analog isolation circuit for all ADC input pins that are to be used by writing a 1 to the appropriate bits of the **GPIOAMSEL** register (see page 686) in the associated GPIO block.

6. If required by the application, reconfigure the sample sequencer priorities in the **ADCSSPRI** register. The default configuration has Sample Sequencer 0 with the highest priority and Sample Sequencer 3 as the lowest priority.

13.4.2 Sample Sequencer Configuration

Configuration of the sample sequencers is slightly more complex than the module initialization because each sample sequencer is completely programmable.

The configuration for each sample sequencer should be as follows:

- Ensure that the sample sequencer is disabled by clearing the corresponding ASENn bit in the ADCACTSS register. Programming of the sample sequencers is allowed without having them enabled. Disabling the sequencer during programming prevents erroneous execution if a trigger event were to occur during the configuration process.
- 2. Configure the trigger event for the sample sequencer in the ADCEMUX register.
- **3.** For each sample in the sample sequence, configure the corresponding input source in the **ADCSSMUXn** and **ADCSSEMUXn** registers.
- **4.** For each sample in the sample sequence, configure the sample control bits in the corresponding nibble in the **ADCSSCTLn** register. When programming the last nibble, ensure that the END bit is set. Failure to set the END bit causes unpredictable behavior.
- 5. If interrupts are to be used, set the corresponding MASK bit in the ADCIM register.
- **6.** Enable the sample sequencer logic by setting the corresponding ASENn bit in the **ADCACTSS** register.

13.5 Register Map

Table 13-4 on page 818 lists the ADC registers. The offset listed is a hexadecimal increment to the register's address, relative to that ADC module's base address of:

ADC0: 0x4003.8000ADC1: 0x4003.9000

Note that the ADC module clock must be enabled before the registers can be programmed (see page 343). There must be a delay of 3 system clocks after the ADC module clock is enabled before any ADC module registers are accessed.

Table 13-4. ADC Register Map

Offset	Name	Type	Reset	Description	See page
0x000	ADCACTSS	R/W	0x0000.0000	ADC Active Sample Sequencer	821
0x004	ADCRIS	RO	0x0000.0000	ADC Raw Interrupt Status	823
0x008	ADCIM	R/W	0x0000.0000	ADC Interrupt Mask	825
0x00C	ADCISC	R/W1C	0x0000.0000	ADC Interrupt Status and Clear	828
0x010	ADCOSTAT	R/W1C	0x0000.0000	ADC Overflow Status	831
0x014	ADCEMUX	R/W	0x0000.0000	ADC Event Multiplexer Select	833

Table 13-4. ADC Register Map (continued)

Offset	Name	Туре	Reset	Description	See page		
0x018	ADCUSTAT	R/W1C	0x0000.0000	ADC Underflow Status	838		
0x01C	ADCTSSEL	R/W	0x0000.0000	ADC Trigger Source Select	839		
0x020	ADCSSPRI	R/W	0x0000.3210	ADC Sample Sequencer Priority	841		
0x024	ADCSPC	R/W	0x0000.0000	ADC Sample Phase Control	843		
0x028	ADCPSSI	R/W	-	ADC Processor Sample Sequence Initiate	845		
0x030	ADCSAC	R/W	0x0000.0000	ADC Sample Averaging Control	847		
0x034	ADCDCISC	R/W1C	0x0000.0000	ADC Digital Comparator Interrupt Status and Clear	848		
0x038	ADCCTL	R/W	0x0000.0000	ADC Control	850		
0x040	ADCSSMUX0	R/W	0x0000.0000	ADC Sample Sequence Input Multiplexer Select 0	851		
0x044	ADCSSCTL0	R/W	0x0000.0000	ADC Sample Sequence Control 0	853		
0x048	ADCSSFIFO0	RO	-	ADC Sample Sequence Result FIFO 0	860		
0x04C	ADCSSFSTAT0	RO	0x0000.0100	ADC Sample Sequence FIFO 0 Status	861		
0x050	ADCSSOP0	R/W	0x0000.0000	ADC Sample Sequence 0 Operation	863		
0x054	ADCSSDC0	R/W	0x0000.0000	ADC Sample Sequence 0 Digital Comparator Select	865		
0x058	ADCSSEMUX0	R/W	0x0000.0000	ADC Sample Sequence Extended Input Multiplexer Select 0			
0x060	ADCSSMUX1	R/W	0x0000.0000	ADC Sample Sequence Input Multiplexer Select 1	869		
0x064	ADCSSCTL1	R/W	0x0000.0000	ADC Sample Sequence Control 1	870		
0x068	ADCSSFIFO1	RO	-	ADC Sample Sequence Result FIFO 1	860		
0x06C	ADCSSFSTAT1	RO	0x0000.0100	ADC Sample Sequence FIFO 1 Status	861		
0x070	ADCSSOP1	R/W	0x0000.0000	ADC Sample Sequence 1 Operation	874		
0x074	ADCSSDC1	R/W	0x0000.0000	ADC Sample Sequence 1 Digital Comparator Select	875		
0x078	ADCSSEMUX1	R/W	0x0000.0000	ADC Sample Sequence Extended Input Multiplexer Select 1	877		
0x080	ADCSSMUX2	R/W	0x0000.0000	ADC Sample Sequence Input Multiplexer Select 2	869		
0x084	ADCSSCTL2	R/W	0x0000.0000	ADC Sample Sequence Control 2	870		
0x088	ADCSSFIFO2	RO	-	ADC Sample Sequence Result FIFO 2	860		
0x08C	ADCSSFSTAT2	RO	0x0000.0100	ADC Sample Sequence FIFO 2 Status	861		
0x090	ADCSSOP2	R/W	0x0000.0000	ADC Sample Sequence 2 Operation	874		
0x094	ADCSSDC2	R/W	0x0000.0000	ADC Sample Sequence 2 Digital Comparator Select	875		
0x098	ADCSSEMUX2	R/W	0x0000.0000	ADC Sample Sequence Extended Input Multiplexer Select 2	877		
0x0A0	ADCSSMUX3	R/W	0x0000.0000	ADC Sample Sequence Input Multiplexer Select 3	879		

Table 13-4. ADC Register Map (continued)

Offset	Name	Туре	Reset	Description	See page
0x0A4	ADCSSCTL3	R/W	0x0000.0000	ADC Sample Sequence Control 3	880
0x0A8	ADCSSFIFO3	RO	-	ADC Sample Sequence Result FIFO 3	860
0x0AC	ADCSSFSTAT3	RO	0x0000.0100	ADC Sample Sequence FIFO 3 Status	861
0x0B0	ADCSSOP3	R/W	0x0000.0000	ADC Sample Sequence 3 Operation	882
0x0B4	ADCSSDC3	R/W	0x0000.0000	ADC Sample Sequence 3 Digital Comparator Select	883
0x0B8	ADCSSEMUX3	R/W	0x0000.0000	ADC Sample Sequence Extended Input Multiplexer Select 3	884
0xD00	ADCDCRIC	WO	0x0000.0000	ADC Digital Comparator Reset Initial Conditions	885
0xE00	ADCDCCTL0	R/W	0x0000.0000	ADC Digital Comparator Control 0	890
0xE04	ADCDCCTL1	R/W	0x0000.0000	ADC Digital Comparator Control 1	890
0xE08	ADCDCCTL2	R/W	0x0000.0000	ADC Digital Comparator Control 2	890
0xE0C	ADCDCCTL3	R/W	0x0000.0000	ADC Digital Comparator Control 3	890
0xE10	ADCDCCTL4	R/W	0x0000.0000	ADC Digital Comparator Control 4	890
0xE14	ADCDCCTL5	R/W	0x0000.0000	ADC Digital Comparator Control 5	890
0xE18	ADCDCCTL6	R/W	0x0000.0000	ADC Digital Comparator Control 6	890
0xE1C	ADCDCCTL7	R/W	0x0000.0000	ADC Digital Comparator Control 7	890
0xE40	ADCDCCMP0	R/W	0x0000.0000	ADC Digital Comparator Range 0	893
0xE44	ADCDCCMP1	R/W	0x0000.0000	ADC Digital Comparator Range 1	893
0xE48	ADCDCCMP2	R/W	0x0000.0000	ADC Digital Comparator Range 2	893
0xE4C	ADCDCCMP3	R/W	0x0000.0000	ADC Digital Comparator Range 3	893
0xE50	ADCDCCMP4	R/W	0x0000.0000	ADC Digital Comparator Range 4	893
0xE54	ADCDCCMP5	R/W	0x0000.0000	ADC Digital Comparator Range 5	893
0xE58	ADCDCCMP6	R/W	0x0000.0000	ADC Digital Comparator Range 6	893
0xE5C	ADCDCCMP7	R/W	0x0000.0000	ADC Digital Comparator Range 7	893
0xFC0	ADCPP	RO	0x00B0.2167	ADC Peripheral Properties	894
0xFC4	ADCPC	R/W	0x0000.0007	ADC Peripheral Configuration	896
0xFC8	ADCCC	R/W	0x0000.0000	ADC Clock Configuration	897

13.6 Register Descriptions

The remainder of this section lists and describes the ADC registers, in numerical order by address offset.

Register 1: ADC Active Sample Sequencer (ADCACTSS), offset 0x000


This register controls the activation of the sample sequencers. Each sample sequencer can be enabled or disabled independently.

ADC Active Sample Sequencer (ADCACTSS)

ADC0 base: 0x4003.8000 ADC1 base: 0x4003.9000

Offset 0x000

Type R/W, reset 0x0000.0000



Bit/Field	Name	Type	Reset	Description
1	ASEN1	R/W	0	ADC SS1 Enable
				Value Description O Sample Sequencer 1 is disabled. Sample Sequencer 1 is enabled.
0	ASEN0	R/W	0	ADC SS0 Enable Value Description 0 Sample Sequencer 0 is disabled. 1 Sample Sequencer 0 is enabled.

Register 2: ADC Raw Interrupt Status (ADCRIS), offset 0x004


This register shows the status of the raw interrupt signal of each sample sequencer. These bits may be polled by software to look for interrupt conditions without sending the interrupts to the interrupt controller.

ADC Raw Interrupt Status (ADCRIS)

ADC0 base: 0x4003.8000 ADC1 base: 0x4003.9000

Offset 0x004

Type RO, reset 0x0000.0000



Bit/Field	Name	Type	Reset	Description
31:17	reserved	RO	0x000	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
16	INRDC	RO	0	Digital Comparator Raw Interrupt Status
				Value Description
				0 All bits in the ADCDCISC register are clear.
				1 At least one bit in the ADCDCISC register is set, meaning that a digital comparator interrupt has occurred.
15:4	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
3	INR3	RO	0	SS3 Raw Interrupt Status
				Value Description
				0 An interrupt has not occurred.
				A sample has completed conversion and the respective ADCSSCTL3 IEn bit is set, enabling a raw interrupt.
				This bit is cleared by writing a 1 to the ${\tt IN3}$ bit in the ADCISC register.
2	INR2	RO	0	SS2 Raw Interrupt Status
				Value Description

This bit is cleared by writing a 1 to the ${\tt IN2}$ bit in the ADCISC register.

A sample has completed conversion and the respective **ADCSSCTL2** IEn bit is set, enabling a raw interrupt.

An interrupt has not occurred.

0

1

Bit/Field	Name	Туре	Reset	Description
1	INR1	RO	0	SS1 Raw Interrupt Status
				Value Description
				An interrupt has not occurred.
				A sample has completed conversion and the respective ADCSSCTL1 IEn bit is set, enabling a raw interrupt.
				This bit is cleared by writing a 1 to the ${\tt IN1}$ bit in the ADCISC register.
0	INR0	RO	0	SS0 Raw Interrupt Status
				Value Description
				0 An interrupt has not occurred.
				A sample has completed conversion and the respective ADCSSCTL0 IEn bit is set, enabling a raw interrupt.

This bit is cleared by writing a 1 to the ${\tt INO}$ bit in the **ADCISC** register.

Register 3: ADC Interrupt Mask (ADCIM), offset 0x008


This register controls whether the sample sequencer and digital comparator raw interrupt signals are sent to the interrupt controller. Each raw interrupt signal can be masked independently.

Only a single DCONSSn bit should be set at any given time. Setting more than one of these bits results in the INRDC bit from the ADCRIS register being masked, and no interrupt is generated on any of the sample sequencer interrupt lines. It is recommended that when interrupts are used, they are enabled on alternating samples or at the end of the sample sequence.

ADC Interrupt Mask (ADCIM)

ADC0 base: 0x4003.8000 ADC1 base: 0x4003.9000 Offset 0x008

Type R/W, reset 0x0000.0000



Value Description

- 0 The status of the digital comparators does not affect the SS3 interrupt status.
- The raw interrupt signal from the digital comparators (INRDC bit in the ADCRIS register) is sent to the interrupt controller on the SS3 interrupt line.
- 18 DCONSS2 R/W 0 Digital Comparator Interrupt on SS2

Value Description

- The status of the digital comparators does not affect the SS2 interrupt status.
- The raw interrupt signal from the digital comparators (INRDC bit in the ADCRIS register) is sent to the interrupt controller on the SS2 interrupt line.

Bit/Field	Name	Туре	Reset	Description
17	DCONSS1	R/W	0	Digital Comparator Interrupt on SS1
				Value Description
				0 The status of the digital comparators does not affect the SS1 interrupt status.
				The raw interrupt signal from the digital comparators (INRDC bit in the ADCRIS register) is sent to the interrupt controller on the SS1 interrupt line.
16	DCONSS0	R/W	0	Digital Comparator Interrupt on SS0
				Value Description
				The status of the digital comparators does not affect the SS0 interrupt status.
				The raw interrupt signal from the digital comparators (INRDC bit in the ADCRIS register) is sent to the interrupt controller on the SS0 interrupt line.
15:4	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
3	MASK3	R/W	0	SS3 Interrupt Mask
				Value Description
				0 The status of Sample Sequencer 3 does not affect the SS3 interrupt status.
				1 The raw interrupt signal from Sample Sequencer 3 (ADCRIS register INR3 bit) is sent to the interrupt controller.
2	MASK2	R/W	0	SS2 Interrupt Mask
				Value Description
				O The status of Sample Sequencer 2 does not affect the SS2 interrupt status.
				1 The raw interrupt signal from Sample Sequencer 2 (ADCRIS register INR2 bit) is sent to the interrupt controller.
1	MASK1	R/W	0	SS1 Interrupt Mask
				Value Description
				The status of Sample Sequencer 1 does not affect the SS1 interrupt status.
				The raw interrupt signal from Sample Sequencer 1 (ADCRIS register INR1 bit) is sent to the interrupt controller.

Bit/Field	Name	Туре	Reset	Description			
0	MASK0	R/W	0	SS0 Interrupt Mask			
				Value Description			
				0 The status of Sample Sequencer 0 does not affect the SS0 interrupt status.			
				1 The raw interrupt signal from Sample Sequencer 0 (ADCRIS register INR0 bit) is sent to the interrupt controller.			

February 20, 2013 827

Register 4: ADC Interrupt Status and Clear (ADCISC), offset 0x00C

This register provides the mechanism for clearing sample sequencer interrupt conditions and shows the status of interrupts generated by the sample sequencers and the digital comparators which have been sent to the interrupt controller. When read, each bit field is the logical AND of the respective INR and MASK bits. Sample sequencer interrupts are cleared by writing a 1 to the corresponding bit position. Digital comparator interrupts are cleared by writing a 1 to the appropriate bits in the **ADCDCISC** register. If software is polling the **ADCRIS** instead of generating interrupts, the sample sequence INRn bits are still cleared via the **ADCISC** register, even if the INn bit is not set.

ADC Interrupt Status and Clear (ADCISC)

Name

Type

ADC0 base: 0x4003.8000 ADC1 base: 0x4003.9000 Offset 0x00C

Bit/Field

Type R/W1C, reset 0x0000.0000

	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16
		1	1	1		resei	rved	1				1	DCINSS3	DCINSS2	DCINSS1	DCINSS0
Type	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO
Reset	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0
	15	14	13	12	11	10	9	8	7	6	5	4	3	2	1	0
		1	ı	ı		rese	rved	•				!	IN3	IN2	IN1	IN0
Туре	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	R/W1C	R/W1C	R/W1C	R/W1C
Reset	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0

31:20	reserved	RO	0x000	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
19	DCINSS3	RO	0	Digital Comparator Interrupt Status on SS3

Description

Value Description

- 0 No interrupt has occurred or the interrupt is masked.
- Both the INRDC bit in the ADCRIS register and the DCONSS3 bit in the ADCIM register are set, providing a level-based interrupt to the interrupt controller.

This bit is cleared by writing a 1 to it. Clearing this bit also clears the ${\tt INRDC}$ bit in the ${\bf ADCRIS}$ register.

18 DCINSS2 RO 0 Digital Comparator Interrupt Status on SS2

Reset

Value Description

- 0 No interrupt has occurred or the interrupt is masked.
- Both the INRDC bit in the ADCRIS register and the DCONSS2 bit in the ADCIM register are set, providing a level-based interrupt to the interrupt controller.

This bit is cleared by writing a 1 to it. Clearing this bit also clears the INRDC bit in the **ADCRIS** register.

Bit/Field	Name	Туре	Reset	Description
17	DCINSS1	RO	0	Digital Comparator Interrupt Status on SS1
				Value Description
				0 No interrupt has occurred or the interrupt is masked.
				Both the INRDC bit in the ADCRIS register and the DCONSS1 bit in the ADCIM register are set, providing a level-based interrupt to the interrupt controller.
				This bit is cleared by writing a 1 to it. Clearing this bit also clears the INRDC bit in the ADCRIS register.
16	DCINSS0	RO	0	Digital Comparator Interrupt Status on SS0
				Value Description
				0 No interrupt has occurred or the interrupt is masked.
				Both the INRDC bit in the ADCRIS register and the DCONSS0 bit in the ADCIM register are set, providing a level-based interrupt to the interrupt controller.
				This bit is cleared by writing a 1 to it. Clearing this bit also clears the INRDC bit in the ADCRIS register.
15:4	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
3	IN3	R/W1C	0	SS3 Interrupt Status and Clear
				Value Description
				0 No interrupt has occurred or the interrupt is masked.
				1 Both the INR3 bit in the ADCRIS register and the MASK3 bit in the ADCIM register are set, providing a level-based interrupt to the interrupt controller.
				This bit is cleared by writing a 1. Clearing this bit also clears the ${\tt INR3}$ bit in the ${\bf ADCRIS}$ register.
2	IN2	R/W1C	0	SS2 Interrupt Status and Clear
				Value Description
				0 No interrupt has occurred or the interrupt is masked.
				Both the INR2 bit in the ADCRIS register and the MASK2 bit in the ADCIM register are set, providing a level-based interrupt to the interrupt controller.

This bit is cleared by writing a 1. Clearing this bit also clears the ${\tt INR2}$ bit in the ${\bf ADCRIS}$ register.

Bit/Field	Name	Туре	Reset	Description
1	IN1	R/W1C	0	SS1 Interrupt Status and Clear
				 Value Description No interrupt has occurred or the interrupt is masked. Both the INR1 bit in the ADCRIS register and the MASK1 bit in the ADCIM register are set, providing a level-based interrupt to the interrupt controller. This bit is cleared by writing a 1. Clearing this bit also clears the INR1
0	INO	R/W1C	0	bit in the ADCRIS register.
0	IN0	RIWIC	0	Value Description No interrupt has occurred or the interrupt is masked. Both the INR0 bit in the ADCRIS register and the MASK0 bit in the ADCIM register are set, providing a level-based interrupt to the interrupt controller.
				This bit is cleared by writing a 1. Clearing this bit also clears the ${\tt INR0}$ bit in the ADCRIS register.

Register 5: ADC Overflow Status (ADCOSTAT), offset 0x010

This register indicates overflow conditions in the sample sequencer FIFOs. Once the overflow condition has been handled by software, the condition can be cleared by writing a 1 to the corresponding bit position.

ADC Overflow Status (ADCOSTAT)

ADC0 base: 0x4003.8000 ADC1 base: 0x4003.9000

Offset 0x010

Type R/W1C, reset 0x0000.0000



Bit/Field	Name	Type	Reset	Description
31:4	reserved	RO	0x0000.000	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
3	OV3	R/W1C	0	SS3 FIFO Overflow
				Value Description
				0 The FIFO has not overflowed.
				1 The FIFO for Sample Sequencer 3 has hit an overflow condition, meaning that the FIFO is full and a write was requested. When an overflow is detected, the most recent write is dropped.
				This bit is cleared by writing a 1.
2	OV2	R/W1C	0	SS2 FIFO Overflow
				Value Description
				0 The FIFO has not overflowed.
				1 The FIFO for Sample Sequencer 2 has hit an overflow condition, meaning that the FIFO is full and a write was requested. When an overflow is detected, the most recent write is dropped.
				This bit is cleared by writing a 1.
1	OV1	R/W1C	0	SS1 FIFO Overflow
				Value Description
				0 The FIFO has not overflowed.
				1 The FIFO for Sample Sequencer 1 has hit an overflow condition,

This bit is cleared by writing a 1.

meaning that the FIFO is full and a write was requested. When an overflow is detected, the most recent write is dropped.

Bit/Field	Name	Туре	Reset	Description
0	OV0	R/W1C	0	SS0 FIFO Overflow
				 Value Description The FIFO has not overflowed. The FIFO for Sample Sequencer 0 has hit an overflow condition, meaning that the FIFO is full and a write was requested. When an overflow is detected, the most recent write is dropped.


This bit is cleared by writing a 1.

Register 6: ADC Event Multiplexer Select (ADCEMUX), offset 0x014

The **ADCEMUX** selects the event (trigger) that initiates sampling for each sample sequencer. Each sample sequencer can be configured with a unique trigger source. When using a PWM generator as the trigger source, use the **ADC Trigger Source Select (ADCTSSEL)** register to specify in which PWM module the generator is located.

ADC Event Multiplexer Select (ADCEMUX)

ADC0 base: 0x4003.8000 ADC1 base: 0x4003.9000 Offset 0x014



Bit/Field	Name	Type	Reset	Description
31:16	reserved	RO	0x0000	Software sh

Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.

Bit/Field	Name	Туре	Reset	Description	on
15:12	ЕМ3	R/W	0x0	This field	ger Select selects the trigger source for Sample Sequencer 3. configurations for this field are:
				Value	Event
				0x0	Processor (default)
					The trigger is initiated by setting the SSn bit in the ADCPSSI register.
				0x1	Analog Comparator 0
					This trigger is configured by the Analog Comparator Control 0 (ACCTL0) register (page 1231).
				0x2	Analog Comparator 1
					This trigger is configured by the Analog Comparator Control 1 (ACCTL1) register (page 1231).
				0x3	Analog Comparator 2
					This trigger is configured by the Analog Comparator Control 2 (ACCTL2) register (page 1231).
				0x4	External (GPIO Pins)
					This trigger is connected to the GPIO interrupt for the corresponding GPIO (see "ADC Trigger Source" on page 653).
				0x5	Timer
					In addition, the trigger must be enabled with the ${\tt TnOTE}$ bit in the GPTMCTL register (page 737).
				0x6	PWM generator 0
					The PWM generator 0 trigger can be configured with the PWM0 Interrupt and Trigger Enable (PWM0INTEN) register (page 1279).
				0x7	PWM generator 1
					The PWM generator 1 trigger can be configured with the PWM1INTEN register (page 1279).
				8x0	PWM generator 2
					The PWM generator 2 trigger can be configured with the PWM2INTEN register (page 1279).
				0x9	PWM generator 3
					The PWM generator 3 trigger can be configured with the PWM3INTEN register (page 1279).
				0xA-0xE	reserved
				0xF	Always (continuously sample)

Bit/Field	Name	Туре	Reset	Description	on
11:8	EM2	R/W	0x0	This field	ger Select selects the trigger source for Sample Sequencer 2. configurations for this field are:
				Value	Event
				0x0	Processor (default)
					The trigger is initiated by setting the SSn bit in the ADCPSSI register.
				0x1	Analog Comparator 0
					This trigger is configured by the Analog Comparator Control 0 (ACCTL0) register (page 1231).
				0x2	Analog Comparator 1
					This trigger is configured by the Analog Comparator Control 1 (ACCTL1) register (page 1231).
				0x3	Analog Comparator 2
					This trigger is configured by the Analog Comparator Control 2 (ACCTL2) register (page 1231).
				0x4	External (GPIO Pins)
					This trigger is connected to the GPIO interrupt for the corresponding GPIO (see "ADC Trigger Source" on page 653).
				0x5	Timer
					In addition, the trigger must be enabled with the ${ t TnOTE}$ bit in the GPTMCTL register (page 737).
				0x6	PWM generator 0
					The PWM generator 0 trigger can be configured with the PWM0 Interrupt and Trigger Enable (PWM0INTEN) register (page 1279).
				0x7	PWM generator 1
					The PWM generator 1 trigger can be configured with the PWM1INTEN register (page 1279).
				0x8	PWM generator 2
					The PWM generator 2 trigger can be configured with the PWM2INTEN register (page 1279).
				0x9	PWM generator 3
					The PWM generator 3 trigger can be configured with the PWM3INTEN register (page 1279).
				0xA-0xE	reserved
				0xF	Always (continuously sample)

Bit/Field	Name	Туре	Reset	Description				
7:4	EM1	R/W	0x0	SS1 Trigger Select				
				This field	selects the trigger source for Sample Sequencer 1.			
				The valid	configurations for this field are:			
				Value	Event			
				0x0	Processor (default)			
					The trigger is initiated by setting the \mathtt{SSn} bit in the ADCPSSI register.			
				0x1	Analog Comparator 0			
					This trigger is configured by the Analog Comparator Control 0 (ACCTL0) register (page 1231).			
				0x2	Analog Comparator 1			
					This trigger is configured by the Analog Comparator Control 1 (ACCTL1) register (page 1231).			
				0x3	Analog Comparator 2			
					This trigger is configured by the Analog Comparator Control 2 (ACCTL2) register (page 1231).			
				0x4	External (GPIO Pins)			
					This trigger is connected to the GPIO interrupt for the corresponding GPIO (see "ADC Trigger Source" on page 653).			
				0x5	Timer			
					In addition, the trigger must be enabled with the ${ t TnOTE}$ bit in the GPTMCTL register (page 737).			
				0x6	PWM generator 0			
					The PWM generator 0 trigger can be configured with the PWM0 Interrupt and Trigger Enable (PWM0INTEN) register (page 1279).			
				0x7	PWM generator 1			
					The PWM generator 1 trigger can be configured with the PWM1INTEN register (page 1279).			
				0x8	PWM generator 2			
					The PWM generator 2 trigger can be configured with the PWM2INTEN register (page 1279).			
				0x9	PWM generator 3			
					The PWM generator 3 trigger can be configured with the PWM3INTEN register (page 1279).			
				0xA-0xE	reserved			
				0xF	Always (continuously sample)			

Bit/Field	Name	Туре	Reset	Description	no
3:0	EM0	R/W	0x0	This field	ger Select selects the trigger source for Sample Sequencer 0 configurations for this field are:
				Value	Event
				0x0	Processor (default)
				ONO	The trigger is initiated by setting the SSn bit in the ADCPSSI register.
				0x1	Analog Comparator 0
					This trigger is configured by the Analog Comparator Control 0 (ACCTL0) register (page 1231).
				0x2	Analog Comparator 1
					This trigger is configured by the Analog Comparator Control 1 (ACCTL1) register (page 1231).
				0x3	Analog Comparator 2
					This trigger is configured by the Analog Comparator Control 2 (ACCTL2) register (page 1231).
				0x4	External (GPIO Pins)
					This trigger is connected to the GPIO interrupt for the corresponding GPIO (see "ADC Trigger Source" on page 653).
				0x5	Timer
					In addition, the trigger must be enabled with the ${ t TnOTE}$ bit in the GPTMCTL register (page 737).
				0x6	PWM generator 0
					The PWM generator 0 trigger can be configured with the PWM0 Interrupt and Trigger Enable (PWM0INTEN) register (page 1279).
				0x7	PWM generator 1
					The PWM generator 1 trigger can be configured with the PWM1INTEN register (page 1279).
				0x8	PWM generator 2
					The PWM generator 2 trigger can be configured with the PWM2INTEN register (page 1279).
				0x9	PWM generator 3
					The PWM generator 3 trigger can be configured with the PWM3INTEN register (page 1279).
				0xA-0xE	reserved
				0xF	Always (continuously sample)

Register 7: ADC Underflow Status (ADCUSTAT), offset 0x018

This register indicates underflow conditions in the sample sequencer FIFOs. The corresponding underflow condition is cleared by writing a 1 to the relevant bit position.

ADC Underflow Status (ADCUSTAT)


UV0

R/W1C

0

ADC0 base: 0x4003.8000 ADC1 base: 0x4003.9000 Offset 0x018

Type R/W1C, reset 0x0000.0000



Bit/Field	Name	Type	Reset	Description
31:4	reserved	RO	0x0000.000	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
3	UV3	R/W1C	0	SS3 FIFO Underflow
				The valid configurations for this field are shown below. This bit is cleared by writing a 1.
				Value Description
				0 The FIFO has not underflowed.
				The FIFO for the Sample Sequencer has hit an underflow condition, meaning that the FIFO is empty and a read was requested. The problematic read does not move the FIFO pointers, and 0s are returned.
2	UV2	R/W1C	0	SS2 FIFO Underflow
				The valid configurations are the same as those for the ${\tt UV3}$ field. This bit is cleared by writing a 1.
1	UV1	R/W1C	0	SS1 FIFO Underflow
				The valid configurations are the same as those for the ${\tt UV3}$ field. This bit is cleared by writing a 1.

SS0 FIFO Underflow

bit is cleared by writing a 1.

The valid configurations are the same as those for the UV3 field. This

838 February 20, 2013

Register 8: ADC Trigger Source Select (ADCTSSEL), offset 0x01C

The ADCTSSEL register specifies which PWM module is selected with the EMn bit field in the ADC Event Multiplexer Select (ADCEMUX) register. The register resets to 0x0000.0000, which selects PWM module 0 for all generators.

ADC Trigger Source Select (ADCTSSEL)

ADC0 base: 0x4003.8000 ADC1 base: 0x4003.9000 Offset 0x01C

Type R/W, reset 0x0000.0000

_	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16
[rese	rved	P	S3	'		reser	rved	d I		PS2		reserved		rved	
Type Reset	RO 0	RO 0	R/W 0	R/W 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	R/W 0	R/W 0	RO 0	RO 0	RO 0	RO 0
	15	14	13	12	11	10	9	8	7	6	5	4	3	2	1	0
[rese	rved	PS	S1			reser	rved	1	'	P	I S0		rese	rved	
Туре	RO	RO	R/W	R/W	RO	RO	RO	RO	RO	RO	R/W	R/W	RO	RO	RO	RO
Reset	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0
В	it/Field		Nam	ne	Ty	pe	Reset	Des	cription							
	31:30		rocom	, ad	D	^	0.40	Coff	wara ah	ould not	ralu an t	ha valua	of a roo	on and hit	To prov	ido
	31:30		reserv	/ea	RO		0x0	com	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.							
	29:28		PS:	3	R/	W	0x0	EM	3 PWM N	Module S	elect					
										lects whi //3 encod			•			ld.
								Val	ue D	escriptio	n					
								0x0) F	WM mod	dule 0					
								0x1	F	WM mod	dule 1					
								0x2	2 - 0x3 r	eserved						
	27:22		reserv	ved	R	0	0x0	com	patibility	ould not with futu	ıre prod	ucts, the	value of	a reserv		
	21:20		PS	2	R/	W	0x0	EM2	2 PWM I	Module S	elect					
										lects whi //3 encod			-			ld.
								Val	ue D	escriptio	n					
								0x0) F	WM mod	dule 0					
								0x1	F	WM mod	dule 1					
								0x2	2 - 0x3 r	eserved						
	19:14		reserv	ved .	R	0	0x0			ould not						

preserved across a read-modify-write operation.

Bit/Field	Name	Туре	Reset	Description
13:12	PS1	R/W	0x0	EM1 PWM Module Select
				This field selects which PWM module signals are used in the PWM0-PWM3 encodings of the ADCEMUX register EM1 bit field.
				Value Description
				0x0 PWM module 0
				0x1 PWM module 1
				0x2 - 0x3 reserved
11:6	reserved	RO	0x0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
5:4	PS0	R/W	0x0	EM0 PWM Module Select
				This field selects which PWM module signals are used in the PWM0-PWM3 encodings of the ADCEMUX register ${\tt EM0}$ bit field.
				Value Description
				0x0 PWM module 0
				0x1 PWM module 1
				0x2 - 0x3 reserved
3:0	reserved	RO	0x0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.


Register 9: ADC Sample Sequencer Priority (ADCSSPRI), offset 0x020

This register sets the priority for each of the sample sequencers. Out of reset, Sequencer 0 has the highest priority, and Sequencer 3 has the lowest priority. When reconfiguring sequence priorities, each sequence must have a unique priority for the ADC to operate properly.

ADC Sample Sequencer Priority (ADCSSPRI)

ADC0 base: 0x4003.8000 ADC1 base: 0x4003.9000 Offset 0x020

Type R/W, reset 0x0000.3210



Bit/Field	Name	Туре	Reset	Description
31:14	reserved	RO	0x0000.0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
13:12	SS3	R/W	0x3	SS3 Priority This field contains a binary-encoded value that specifies the priority encoding of Sample Sequencer 3. A priority encoding of 0x0 is highest and 0x3 is lowest. The priorities assigned to the sequencers must be uniquely mapped. The ADC may not operate properly if two or more fields are equal.
11:10	reserved	RO	0x0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
9:8	SS2	R/W	0x2	SS2 Priority This field contains a binary-encoded value that specifies the priority encoding of Sample Sequencer 2. A priority encoding of 0x0 is highest and 0x3 is lowest. The priorities assigned to the sequencers must be uniquely mapped. The ADC may not operate properly if two or more fields are equal.
7:6	reserved	RO	0x0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
5:4	SS1	R/W	0x1	SS1 Priority This field contains a binary-encoded value that specifies the priority encoding of Sample Sequencer 1. A priority encoding of 0x0 is highest and 0x3 is lowest. The priorities assigned to the sequencers must be uniquely mapped. The ADC may not operate properly if two or more fields are equal.
3:2	reserved	RO	0x0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.

Bit/Field	Name	Type	Reset	Description
1:0	SS0	R/W	0x0	SS0 Priority This field contains a binary-encoded value that specifies the priority encoding of Sample Sequencer 0. A priority encoding of 0x0 is highest and 0x3 is lowest. The priorities assigned to the sequencers must be uniquely mapped. The ADC may not operate properly if two or more fields are equal.


Register 10: ADC Sample Phase Control (ADCSPC), offset 0x024

This register allows the ADC module to sample at one of 16 different discrete phases from 0.0° through 337.5°. For example, the sample rate could be effectively doubled by sampling a signal using one ADC module configured with the standard sample time and the second ADC module configured with a 180.0° phase lag.

Note: Care should be taken when the PHASE field is non-zero, as the resulting delay in sampling the AINx input may result in undesirable system consequences. The time from ADC trigger to sample is increased and could make the response time longer than anticipated. The added latency could have ramifications in the system design. Designers should carefully consider the impact of this delay.

ADC Sample Phase Control (ADCSPC)

ADC0 base: 0x4003.8000 ADC1 base: 0x4003.9000 Offset 0x024



Bit/Field Name Type Reset

31:4 reserved RO 0x0000.000

Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.

Bit/Field	Name	Туре	Reset	Description
3:0	PHASE	R/W	0x0	Phase Difference This field selects the sample phase difference from the standard sample time.
				Value Description
				0x0 ADC sample lags by 0.0°
				0x1 ADC sample lags by 22.5°
				0x2 ADC sample lags by 45.0°
				0x3 ADC sample lags by 67.5°
				0x4 ADC sample lags by 90.0°
				0x5 ADC sample lags by 112.5°
				0x6 ADC sample lags by 135.0°
				0x7 ADC sample lags by 157.5°
				0x8 ADC sample lags by 180.0°
				0x9 ADC sample lags by 202.5°
				0xA ADC sample lags by 225.0°
				0xB ADC sample lags by 247.5°
				0xC ADC sample lags by 270.0°
				0xD ADC sample lags by 292.5°
				0xE ADC sample lags by 315.0°
				0xF ADC sample lags by 337.5°

Register 11: ADC Processor Sample Sequence Initiate (ADCPSSI), offset 0x028

This register provides a mechanism for application software to initiate sampling in the sample sequencers. Sample sequences can be initiated individually or in any combination. When multiple sequences are triggered simultaneously, the priority encodings in **ADCSSPRI** dictate execution order.

This register also provides a means to configure and then initiate concurrent sampling on all ADC modules. To do this, the first ADC module should be configured. The **ADCPSSI** register for that module should then be written. The appropriate SS bits should be set along with the SYNCWAIT bit. Additional ADC modules should then be configured following the same procedure. Once the final ADC module is configured, its **ADCPSSI** register should be written with the appropriate SS bits set along with the GSYNC bit. All of the ADC modules then begin concurrent sampling according to their configuration.

ADC Processor Sample Sequence Initiate (ADCPSSI)

ADC0 base: 0x4003.8000 ADC1 base: 0x4003.9000 Offset 0x028 Type R/W, reset -

	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16
	GSYNC		reserved		SYNCWAIT			1			reserved		I			
Type	R/W	RO	RO	RO	R/W	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO
Reset	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0
	15	14	13	12	11	10	9	8	7	6	5	4	3	2	1	0
		reserved									SS3	SS2	SS1	SS0		
Туре	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	WO	WO	WO	wo
Reset	0	0	0	0	0	0	0	0	0	0	0	0	-	-	-	-

Bit/Field	Name	Type	Reset	Description
31	GSYNC	R/W	0	Global Synchronize
				Value Description
				O This bit is cleared once sampling has been initiated.
				This bit initiates sampling in multiple ADC modules at the same time. Any ADC module that has been initialized by setting an SSn bit and the SYNCWAIT bit starts sampling once this bit is written.
30:28	reserved	RO	0x0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
27	SYNCWAIT	R/W	0	Synchronize Wait
				Value Description
				O Sampling begins when a sample sequence has been initiated.
				This bit allows the sample sequences to be initiated, but delays sampling until the GSYNC bit is set.
26:4	reserved	RO	0x0000.0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.

Bit/Field	Name	Туре	Reset	Description
3	SS3	WO	-	SS3 Initiate
				 Value Description No effect. Begin sampling on Sample Sequencer 3, if the sequencer is enabled in the ADCACTSS register. Only a write by software is valid; a read of this register returns no
2	SS2	WO	-	meaningful data. SS2 Initiate
				Value Description No effect. Begin sampling on Sample Sequencer 2, if the sequencer is enabled in the ADCACTSS register.
1	SS1	WO	-	Only a write by software is valid; a read of this register returns no meaningful data. SS1 Initiate
				Value Description No effect. Begin sampling on Sample Sequencer 1, if the sequencer is enabled in the ADCACTSS register.
				Only a write by software is valid; a read of this register returns no meaningful data.
0	SS0	WO	-	SS0 Initiate
				Value Description No effect. Begin sampling on Sample Sequencer 0, if the sequencer is enabled in the ADCACTSS register. Only a write by software is valid; a read of this register returns no meaningful data.

846 February 20, 2013


Register 12: ADC Sample Averaging Control (ADCSAC), offset 0x030

This register controls the amount of hardware averaging applied to conversion results. The final conversion result stored in the FIFO is averaged from 2 AVG consecutive ADC samples at the specified ADC speed. If AVG is 0, the sample is passed directly through without any averaging. If AVG=6, then 64 consecutive ADC samples are averaged to generate one result in the sequencer FIFO. An AVG=7 provides unpredictable results.

ADC Sample Averaging Control (ADCSAC)

ADC0 base: 0x4003.8000 ADC1 base: 0x4003.9000 Offset 0x030

Type R/W, reset 0x0000.0000



Bit/Field	Name	Туре	Reset	Description
31:3	reserved	RO	0x0000.000	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
2:0	AVG	R/W	0x0	Hardware Averaging Control

Specifies the amount of hardware averaging that will be applied to ADC samples. The AVG field can be any value between 0 and 6. Entering a value of 7 creates unpredictable results.


Value	Description
0x0	No hardware oversampling
0x1	2x hardware oversampling
0x2	4x hardware oversampling
0x3	8x hardware oversampling
0x4	16x hardware oversampling
0x5	32x hardware oversampling
0x6	64x hardware oversampling
0x7	reserved

Register 13: ADC Digital Comparator Interrupt Status and Clear (ADCDCISC), offset 0x034

This register provides status and acknowledgement of digital comparator interrupts. One bit is provided for each comparator.

ADC Digital Comparator Interrupt Status and Clear (ADCDCISC)

ADC0 base: 0x4003.8000 ADC1 base: 0x4003.9000 Offset 0x034 Type R/W1C, reset 0x0000.0000



Bit/Field	Name	Туре	Reset	Description
31:8	reserved	RO	0x0000.00	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
7	DCINT7	R/W1C	0	Digital Comparator 7 Interrupt Status and Clear
				Value Description 0 No interrupt. 1 Digital Comparator 7 has generated an interrupt. This bit is cleared by writing a 1.
6	DCINT6	R/W1C	0	Digital Comparator 6 Interrupt Status and Clear
Ü	BOINTO	TOW TO	Ü	Value Description No interrupt. Digital Comparator 6 has generated an interrupt.
				This bit is cleared by writing a 1.
5	DCINT5	R/W1C	0	Digital Comparator 5 Interrupt Status and Clear Value Description 0 No interrupt. 1 Digital Comparator 5 has generated an interrupt.

This bit is cleared by writing a 1.

Bit/Field	Name	Туре	Reset	Description
4	DCINT4	R/W1C	0	Digital Comparator 4 Interrupt Status and Clear
				Value Description 0 No interrupt. 1 Digital Comparator 4 has generated an interrupt. This bit is cleared by writing a 1.
3	DCINT3	R/W1C	0	Digital Comparator 3 Interrupt Status and Clear
				 Value Description No interrupt. Digital Comparator 3 has generated an interrupt. This bit is cleared by writing a 1.
2	DCINT2	R/W1C	0	Digital Comparator 2 Interrupt Status and Clear
				Value Description No interrupt. Digital Comparator 2 has generated an interrupt. This bit is cleared by writing a 1.
1	DCINT1	R/W1C	0	Digital Comparator 1 Interrupt Status and Clear
				Value Description No interrupt. Digital Comparator 1 has generated an interrupt. This bit is cleared by writing a 1.
0	DCINT0	R/W1C	0	Digital Comparator 0 Interrupt Status and Clear
				Value Description 0 No interrupt. 1 Digital Comparator 0 has generated an interrupt. This bit is cleared by writing a 1.

Register 14: ADC Control (ADCCTL), offset 0x038


This register configures the voltage reference. The voltage references for the conversion can be VREFA+ and VREFA- or VDDA and GNDA.

ADC Control (ADCCTL)

ADC0 base: 0x4003.8000 ADC1 base: 0x4003.9000

Offset 0x038

Type R/W, reset 0x0000.0000



Bit/Field	Name	Туре	Reset	Description
31:7	reserved	RO	0x0000.000	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
6	DITHER	R/W	0	Dither Mode Enable Value Description 0 Dither mode disabled 1 Dither mode enabled
5:2	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
1:0	VREF	R/W	0x0	Voltage Reference Select

Value Description

0x0 VDDA and GNDA are the voltage references.

0x1 - 0x3 The external ${\tt VREFA+}$ and ${\tt VREFA-}$ inputs are the voltage references.

Register 15: ADC Sample Sequence Input Multiplexer Select 0 (ADCSSMUX0), offset 0x040

This register, along with the **ADCSSEMUX0** register, defines the analog input configuration for each sample in a sequence executed with Sample Sequencer 0. If the corresponding \mathtt{EMUXn} bit in the **ADCSSEMUX0** register is set, the \mathtt{MUXn} field in this register selects from $\mathtt{AIN[21:16]}$. When the corresponding \mathtt{EMUXn} bit is clear, the \mathtt{MUXn} field selects from $\mathtt{AIN[15:0]}$. This register is 32 bits wide and contains information for eight possible samples.

Note: Channels AIN[31:22] do not exist on this microcontroller. Configuring MUXn to be 0xA-0xF when the corresponding EMUXn bit is set results in undefined behavior.

ADC Sample Sequence Input Multiplexer Select 0 (ADCSSMUX0)

ADC0 base: 0x4003.8000 ADC1 base: 0x4003.9000 Offset 0x040

Type R/W, reset 0x0000.0000

1 ypc	10,44,1030	o o o o o o o	.0000													
	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16
	'	MU	JX7	ı	MUX6				MUX5			•	MUX4			
Туре	R/W	R/W	R/W	R/W	R/W	R/W	R/W	R/W	R/W	R/W	R/W	R/W	R/W	R/W	R/W	R/W
Reset	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0
	15	14	13	12	11	10	9	8	7	6	5	4	3	2	1	0
		MU	JX3	I		M	UX2			MU	JX1	Ī		MU	JX0	
Type Reset	R/W 0	R/W 0	R/W 0	R/W 0	R/W 0	R/W 0	R/W 0	R/W 0	R/W 0	R/W 0	R/W 0	R/W 0	R/W 0	R/W 0	R/W 0	R/W 0
E	Bit/Field		Nan	ne	Ty	pe	Reset	Des	cription							
	31:28		MUX	(7	R	/W	0x0	8th	Sample	Input Se	lect					
								with sam the c indic the i	the sampled for the corresponding the corresponding the corresponding to the corresponding to the corresponding the corresponding to th	nple sequathe analoonding pions input is AIN17.	uencer. I og-to-digi n, for ex AIN1. A	the eight t specifie tal conve ample, a value of oled (the I to the pa	s which rsion. The value of 0x1 when 07 bit in 1	of the arge value so 0x1 whe en EMUX	. nalog inp et here i n EMUX7 is set ir	outs is indicates is clear indicates register
	27:24		MUX	/G	В	/W	0x0			2i and 2i+ Input Se						
	21.24		WIO	· · ·	IV.	VV	0.00	The exec	MUX6 fie	eld is use th the sa	ed durino mple se	g the sev quencer. llog-to-di	It specif	ies whic		
	23:20		MUX	< 5	R	/W	0x0	6th	Sample	Input Se	lect					
								with	the sam	nple sequ	uencer. I	the sixth t specifie gital conv	s which			
	19:16		MUX	< 4	R	/W	0x0	5th	Sample	Input Se	lect					
								with	the sam	nple sequ	uencer. Ì	g the fifth t specifie gital conv	s which			

Bit/Field	Name	Type	Reset	Description
15:12	MUX3	R/W	0x0	4th Sample Input Select The MUX3 field is used during the fourth sample of a sequence executed with the sample sequencer. It specifies which of the analog inputs is sampled for the analog-to-digital conversion.
11:8	MUX2	R/W	0x0	3rd Sample Input Select The MUX2 field is used during the third sample of a sequence executed with the sample sequencer. It specifies which of the analog inputs is sampled for the analog-to-digital conversion.
7:4	MUX1	R/W	0x0	2nd Sample Input Select The MUX1 field is used during the second sample of a sequence executed with the sample sequencer. It specifies which of the analog inputs is sampled for the analog-to-digital conversion.
3:0	MUX0	R/W	0x0	1st Sample Input Select The MUX0 field is used during the first sample of a sequence executed with the sample sequencer. It specifies which of the analog inputs is sampled for the analog-to-digital conversion.

Register 16: ADC Sample Sequence Control 0 (ADCSSCTL0), offset 0x044

This register contains the configuration information for each sample for a sequence executed with a sample sequencer. When configuring a sample sequence, the END bit must be set for the final sample, whether it be after the first sample, eighth sample, or any sample in between. This register is 32 bits wide and contains information for eight possible samples.

ADC Sample Sequence Control 0 (ADCSSCTL0)

ADC0 base: 0x4003.8000 ADC1 base: 0x4003.9000 Offset 0x044

29

END7

R/W

0

Type R/W, reset 0x0000.0000

_	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16
	TS7	IE7	END7	D7	TS6	IE6	END6	D6	TS5	IE5	END5	D5	TS4	IE4	END4	D4
Туре	R/W	R/W	R/W	R/W												
Reset	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0
	15	14	13	12	11	10	9	8	7	6	5	4	3	2	1	0
	TS3	IE3	END3	D3	TS2	IE2	END2	D2	TS1	IE1	END1	D1	TS0	IE0	END0	D0
Type	R/W	R/W	R/W	R/W												
Reset	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0

Bit/Field	Name	Туре	Reset	Description
31	TS7	R/W	0	8th Sample Temp Sensor Select
				Value Description
				The input pin specified by the ADCSSMUXn register is read during the eighth sample of the sample sequence.
				1 The temperature sensor is read during the eighth sample of the sample sequence.
30	IE7	R/W	0	8th Sample Interrupt Enable
				Value Description
				0 The raw interrupt is not asserted to the interrupt controller.
				The raw interrupt signal (INR0 bit) is asserted at the end of the eighth sample's conversion. If the MASK0 bit in the ADCIM register is set, the interrupt is promoted to the interrupt controller.
				It is legal to have multiple samples within a sequence generate interrupts.

Value Description

8th Sample is End of Sequence

- O Another sample in the sequence is the final sample.
- 1 The eighth sample is the last sample of the sequence.

It is possible to end the sequence on any sample position. Software must set an ${\tt ENDn}$ bit somewhere within the sequence. Samples defined after the sample containing a set ${\tt ENDn}$ bit are not requested for conversion even though the fields may be non-zero.

Bit/Field	Name	Туре	Reset	Description
28	D7	R/W	0	8th Sample Differential Input Select
				Value Description
				0 The analog inputs are not differentially sampled.
				The analog input is differentially sampled. The corresponding ADCSSMUXn nibble must be set to the pair number "i", where the paired inputs are "2i and 2i+1".
				Because the temperature sensor does not have a differential option, this bit must not be set when the ${\tt TS7}$ bit is set.
27	TS6	R/W	0	7th Sample Temp Sensor Select
				Value Description
				The input pin specified by the ADCSSMUXn register is read during the seventh sample of the sample sequence.
				1 The temperature sensor is read during the seventh sample of the sample sequence.
26	IE6	R/W	0	7th Sample Interrupt Enable
				Value Description
				O The raw interrupt is not asserted to the interrupt controller.
				The raw interrupt signal (INR0 bit) is asserted at the end of the seventh sample's conversion. If the MASK0 bit in the ADCIM register is set, the interrupt is promoted to the interrupt controller.
				It is legal to have multiple samples within a sequence generate interrupts.
25	END6	R/W	0	7th Sample is End of Sequence
				Value Description
				O Another sample in the sequence is the final sample.
				1 The seventh sample is the last sample of the sequence.
				It is possible to end the sequence on any sample position. Software must set an ENDn bit somewhere within the sequence. Samples defined after the sample containing a set ENDn bit are not requested for conversion even though the fields may be non-zero.
24	D6	R/W	0	7th Sample Differential Input Select
				Value Description
				0 The analog inputs are not differentially sampled.
				The analog input is differentially sampled. The corresponding ADCSSMUXn nibble must be set to the pair number "i", where the paired inputs are "2i and 2i+1".
				Because the temperature sensor does not have a differential option, this bit must not be set when the TS6 bit is set.

854 February 20, 2013

Bit/Field	Name	Туре	Reset	Description
23	TS5	R/W	0	6th Sample Temp Sensor Select
				Value Description
				The input pin specified by the ADCSSMUXn register is read during the sixth sample of the sample sequence.
				1 The temperature sensor is read during the sixth sample of the sample sequence.
22	IE5	R/W	0	6th Sample Interrupt Enable
				Value Description
				0 The raw interrupt is not asserted to the interrupt controller.
				The raw interrupt signal (INR0 bit) is asserted at the end of the sixth sample's conversion. If the MASK0 bit in the ADCIM register is set, the interrupt is promoted to the interrupt controller.
				It is legal to have multiple samples within a sequence generate interrupts.
21	END5	R/W	0	6th Sample is End of Sequence
				Value Description
				O Another sample in the sequence is the final sample.
				1 The sixth sample is the last sample of the sequence.
				It is possible to end the sequence on any sample position. Software must set an ${\tt ENDn}$ bit somewhere within the sequence. Samples defined after the sample containing a set ${\tt ENDn}$ bit are not requested for conversion even though the fields may be non-zero.
20	D5	R/W	0	6th Sample Differential Input Select
				Value Description
				0 The analog inputs are not differentially sampled.
				The analog input is differentially sampled. The corresponding ADCSSMUXn nibble must be set to the pair number "i", where the paired inputs are "2i and 2i+1".
				Because the temperature sensor does not have a differential option, this bit must not be set when the TS5 bit is set.
19	TS4	R/W	0	5th Sample Temp Sensor Select
				Value Description
				The input pin specified by the ADCSSMUXn register is read during the fifth sample of the sample sequence.
				1 The temperature sensor is read during the fifth sample of the sample sequence.

Bit/Field	Name	Туре	Reset	Description
18	IE4	R/W	0	5th Sample Interrupt Enable
				Value Description
				O The raw interrupt is not asserted to the interrupt controller.
				The raw interrupt signal (INR0 bit) is asserted at the end of the fifth sample's conversion. If the MASK0 bit in the ADCIM register is set, the interrupt is promoted to the interrupt controller.
				It is legal to have multiple samples within a sequence generate interrupts.
17	END4	R/W	0	5th Sample is End of Sequence
				Value Description
				O Another sample in the sequence is the final sample.
				1 The fifth sample is the last sample of the sequence.
				It is possible to end the sequence on any sample position. Software must set an \mathtt{ENDn} bit somewhere within the sequence. Samples defined after the sample containing a set \mathtt{ENDn} bit are not requested for conversion even though the fields may be non-zero.
16	D4	R/W	0	5th Sample Differential Input Select
				Value Description
				0 The analog inputs are not differentially sampled.
				The analog input is differentially sampled. The corresponding ADCSSMUXn nibble must be set to the pair number "i", where the paired inputs are "2i and 2i+1".
				Because the temperature sensor does not have a differential option, this bit must not be set when the ${\tt TS4}$ bit is set.
15	TS3	R/W	0	4th Sample Temp Sensor Select
				Value Description
				The input pin specified by the ADCSSMUXn register is read during the fourth sample of the sample sequence.
				1 The temperature sensor is read during the fourth sample of the sample sequence.
14	IE3	R/W	0	4th Sample Interrupt Enable
				Value Description
				The raw interrupt is not asserted to the interrupt controller.
				The raw interrupt signal (INR0 bit) is asserted at the end of the fourth sample's conversion. If the MASK0 bit in the ADCIM register is set, the interrupt is promoted to the interrupt controller.
				It is legal to have multiple samples within a sequence generate interrupts.

856 February 20, 2013

Bit/Field	Name	Туре	Reset	Description
13	END3	R/W	0	4th Sample is End of Sequence
				Value Description
				O Another sample in the sequence is the final sample.
				1 The fourth sample is the last sample of the sequence.
				It is possible to end the sequence on any sample position. Software must set an ENDn bit somewhere within the sequence. Samples defined after the sample containing a set ENDn bit are not requested for conversion even though the fields may be non-zero.
12	D3	R/W	0	4th Sample Differential Input Select
				Value Description
				0 The analog inputs are not differentially sampled.
				The analog input is differentially sampled. The corresponding ADCSSMUXn nibble must be set to the pair number "i", where the paired inputs are "2i and 2i+1".
				Because the temperature sensor does not have a differential option, this bit must not be set when the ${\tt TS3}$ bit is set.
11	TS2	R/W	0	3rd Sample Temp Sensor Select
				Value Description
				The input pin specified by the ADCSSMUXn register is read during the third sample of the sample sequence.
				1 The temperature sensor is read during the third sample of the sample sequence.
10	IE2	R/W	0	3rd Sample Interrupt Enable
				Value Description
				The raw interrupt is not asserted to the interrupt controller.
				The raw interrupt signal (INR0 bit) is asserted at the end of the third sample's conversion. If the MASK0 bit in the ADCIM register is set, the interrupt is promoted to the interrupt controller.
				It is legal to have multiple samples within a sequence generate interrupts.
9	END2	R/W	0	3rd Sample is End of Sequence
				Value Description
				O Another sample in the sequence is the final sample.
				1 The third sample is the last sample of the sequence.
				It is possible to end the sequence on any sample position. Software must set an \mathtt{ENDn} bit somewhere within the sequence. Samples defined after the sample containing a set \mathtt{ENDn} bit are not requested for conversion even though the fields may be non-zero.

Bit/Field	Name	Туре	Reset	Description
8	D2	R/W	0	3rd Sample Differential Input Select
				Value Description
				0 The analog inputs are not differentially sampled.
				The analog input is differentially sampled. The corresponding ADCSSMUXn nibble must be set to the pair number "i", where the paired inputs are "2i and 2i+1".
				Because the temperature sensor does not have a differential option, this bit must not be set when the ${\tt TS2}$ bit is set.
7	TS1	R/W	0	2nd Sample Temp Sensor Select
				Value Description
				The input pin specified by the ADCSSMUXn register is read during the second sample of the sample sequence.
				1 The temperature sensor is read during the second sample of the sample sequence.
6	IE1	R/W	0	2nd Sample Interrupt Enable
				Value Description
				O The raw interrupt is not asserted to the interrupt controller.
				The raw interrupt signal (INR0 bit) is asserted at the end of the second sample's conversion. If the MASK0 bit in the ADCIM register is set, the interrupt is promoted to the interrupt controller.
				It is legal to have multiple samples within a sequence generate interrupts.
5	END1	R/W	0	2nd Sample is End of Sequence
				Value Description
				O Another sample in the sequence is the final sample.
				1 The second sample is the last sample of the sequence.
				It is possible to end the sequence on any sample position. Software must set an ENDn bit somewhere within the sequence. Samples defined after the sample containing a set ENDn bit are not requested for conversion even though the fields may be non-zero.
4	D1	R/W	0	2nd Sample Differential Input Select
				Value Description
				0 The analog inputs are not differentially sampled.
				The analog input is differentially sampled. The corresponding ADCSSMUXn nibble must be set to the pair number "i", where the paired inputs are "2i and 2i+1".
				Because the temperature sensor does not have a differential option, this bit must not be set when the TS1 bit is set.

858 February 20, 2013

Bit/Field	Name	Туре	Reset	Description
3	TS0	R/W	0	1st Sample Temp Sensor Select
				Value Description
				The input pin specified by the ADCSSMUXn register is read during the first sample of the sample sequence.
				1 The temperature sensor is read during the first sample of the sample sequence.
2	IE0	R/W	0	1st Sample Interrupt Enable
				Value Description
				O The raw interrupt is not asserted to the interrupt controller.
				The raw interrupt signal (INRO bit) is asserted at the end of the first sample's conversion. If the MASKO bit in the ADCIM register is set, the interrupt is promoted to the interrupt controller.
				It is legal to have multiple samples within a sequence generate interrupts.
1	END0	R/W	0	1st Sample is End of Sequence
				Value Description
				O Another sample in the sequence is the final sample.
				1 The first sample is the last sample of the sequence.
				It is possible to end the sequence on any sample position. Software must set an ${\tt ENDn}$ bit somewhere within the sequence. Samples defined after the sample containing a set ${\tt ENDn}$ bit are not requested for conversion even though the fields may be non-zero.
0	D0	R/W	0	1st Sample Differential Input Select
				Value Description
				0 The analog inputs are not differentially sampled.
				The analog input is differentially sampled. The corresponding ADCSSMUXn nibble must be set to the pair number "i", where the paired inputs are "2i and 2i+1".
				Because the temperature sensor does not have a differential option, this bit must not be set when the ${\tt TS0}$ bit is set.


Register 17: ADC Sample Sequence Result FIFO 0 (ADCSSFIFO0), offset 0x048 Register 18: ADC Sample Sequence Result FIFO 1 (ADCSSFIFO1), offset 0x068 Register 19: ADC Sample Sequence Result FIFO 2 (ADCSSFIFO2), offset 0x088 Register 20: ADC Sample Sequence Result FIFO 3 (ADCSSFIFO3), offset 0x0A8

Important: This register is read-sensitive. See the register description for details.

This register contains the conversion results for samples collected with the sample sequencer (the ADCSSFIFO0 register is used for Sample Sequencer 0, ADCSSFIFO1 for Sequencer 1, ADCSSFIFO2 for Sequencer 2, and ADCSSFIFO3 for Sequencer 3). Reads of this register return conversion result data in the order sample 0, sample 1, and so on, until the FIFO is empty. If the FIFO is not properly handled by software, overflow and underflow conditions are registered in the ADCOSTAT and ADCUSTAT registers.

ADC Sample Sequence Result FIFO n (ADCSSFIFOn)

ADC0 base: 0x4003.8000 ADC1 base: 0x4003.9000 Offset 0x048



Bit/Field	Name	Туре	Reset	Description
31:12	reserved	RO	0x0000.0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
11:0	DATA	RO	_	Conversion Result Data

Register 21: ADC Sample Sequence FIFO 0 Status (ADCSSFSTAT0), offset 0x04C

Register 22: ADC Sample Sequence FIFO 1 Status (ADCSSFSTAT1), offset 0x06C

Register 23: ADC Sample Sequence FIFO 2 Status (ADCSSFSTAT2), offset 0x08C

Register 24: ADC Sample Sequence FIFO 3 Status (ADCSSFSTAT3), offset 0x0AC

This register provides a window into the sample sequencer, providing full/empty status information as well as the positions of the head and tail pointers. The reset value of 0x100 indicates an empty FIFO with the head and tail pointers both pointing to index 0. The **ADCSSFSTAT0** register provides status on FIFO0, which has 8 entries; **ADCSSFSTAT1** on FIFO1, which has 4 entries;

ADCSSFSTAT2 on FIFO2, which has 4 entries; and **ADCSSFSTAT3** on FIFO3 which has a single entry.

ADC Sample Sequence FIFO n Status (ADCSSFSTATn)

ADC0 base: 0x4003.8000 ADC1 base: 0x4003.9000 Offset 0x04C Type RO, reset 0x0000.0100

	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16
				•	' !	' '		rese	rved	'						•
Type •	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO
Reset	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0
	15	14	13	12	11	10	9	8	7	6	5	4	3	2	1	0
		reserved		FULL		reserved		EMPTY		HP	TR	ı		TP	TR	
Туре	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO
Reset	0	0	0	0	0	0	0	1	0	0	0	0	0	0	0	0

Bit/Field	Name	Туре	Reset	Description						
31:13	reserved	RO	0x0000.0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.						
12	FULL	RO	0	FIFO Full						
				Value Description The FIFO is not currently full. The FIFO is currently full.						
11:9	reserved	RO	0x0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.						
8	EMPTY	RO	1	FIFO Empty						
				Value Description						

0

The FIFO is not currently empty.

The FIFO is currently empty.

Bit/Field	Name	Type	Reset	Description
7:4	HPTR	RO	0x0	FIFO Head Pointer
				This field contains the current "head" pointer index for the FIFO, that is, the next entry to be written.
				Valid values are 0x0-0x7 for FIFO0; 0x0-0x3 for FIFO1 and FIFO2; and 0x0 for FIFO3.
3:0	TPTR	RO	0x0	FIFO Tail Pointer
				This field contains the current "tail" pointer index for the FIFO, that is, the next entry to be read.
				Valid values are 0x0-0x7 for FIFO0; 0x0-0x3 for FIFO1 and FIFO2; and 0x0 for FIFO3.

20

19

18

17

16

Register 25: ADC Sample Sequence 0 Operation (ADCSSOP0), offset 0x050

This register determines whether the sample from the given conversion on Sample Sequence 0 is saved in the Sample Sequence FIFO0 or sent to the digital comparator unit.

ADC Sample Sequence 0 Operation (ADCSSOP0)

28

26

ADC0 base: 0x4003.8000 ADC1 base: 0x4003.9000 Offset 0x050

31

Type R/W, reset 0x0000.0000

30

	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16
		reserved		S7DCOP		reserved		S6DCOP		reserved		S5DCOP		reserved		S4DCOP
Type Reset	RO 0	RO 0	RO 0	R/W 0	RO 0	RO 0	RO 0	R/W 0	RO 0	RO 0	RO 0	R/W 0	RO 0	RO 0	RO 0	R/W 0
	15	14	13	12	11	10	9	8	7	6	5	4	3	2	1	0
ſ		reserved		S3DCOP		reserved		S2DCOP		reserved		S1DCOP		reserved		SODCOP
Type Reset	RO 0	RO 0	RO 0	R/W 0	RO 0	RO 0	RO 0	R/W 0	RO 0	RO 0	RO 0	R/W 0	RO 0	RO 0	RO 0	R/W 0
Nosci	Ü	Ü	Ü	Ü	Ü	Ü	Ü	Ü	Ü	Ü	Ü	v	o	v	Ü	Ü
В	it/Field		Nar	ne	Ту	ре	Reset	Des	cription							
	31:29		reser	hav	R	.0	0x0	Soft	ware sh	ould not r	elv on t	the value	of a res	served bit.	To pro	vide
	31.29		16361	veu	1	.0	0.00	com	patibility	with futu	re prod		value o	f a reserve		
	28		S7D0	COP	R	W	0	Sam	ple 7 D	igital Com	parato	r Operatio	n			
								Valu	ue Desc	cription						
								0	The	eighth sa	mple is	saved in	Sample	e Sequenc	e FIFC	00.
								1	by th		EL bit iı	n the ADC		comparato o register,		
	27:25		reser	ved	R	0	0x0	com	patibility	with futu	re prod		value o	served bit. f a reserve on.		
	24		S6D0	COP	R	W	0	Sam	ple 6 D	igital Com	parato	r Operatio	n			
								Sam	ne defini	tion as s7	DCOP I	but used o	during t	he sevent	h samp	ole.
	23:21		reserved		R	.0	0x0	com	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should preserve across a read-modify-write operation.							
	20		S5D0	OP	R	W	0	Sam	ple 5 D	igital Com	parato	r Operation	n			
								Sam	ne defini	tion as s7	DCOP I	but used o	during t	he sixth sa	ample.	
	19:17		reser	ved	R	0	0x0	com	patibility	with futu	re prod		value o	served bit. f a reserve on.		
	16		S4D0	COP	R	W	0	Sam	ple 4 D	igital Com	parato	r Operatio	n			
								Sam	ne defini	tion as S7	DCOP I	but used o	during t	he fifth sa	mple.	
	15:13		reser	ved	R	0	0x0	com	patibility	with futu	re prod		value o	served bit. f a reserve on.		

Bit/Field	Name	Type	Reset	Description
12	S3DCOP	R/W	0	Sample 3 Digital Comparator Operation Same definition as S7DCOP but used during the fourth sample.
11:9	reserved	RO	0x0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
8	S2DCOP	R/W	0	Sample 2 Digital Comparator Operation
				Same definition as S7DCOP but used during the third sample.
7:5	reserved	RO	0x0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
4	S1DCOP	R/W	0	Sample 1 Digital Comparator Operation
				Same definition as ${\tt S7DCOP}$ but used during the second sample.
3:1	reserved	RO	0x0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
0	SODCOP	R/W	0	Sample 0 Digital Comparator Operation
				Same definition as S7DCOP but used during the first sample.

Register 26: ADC Sample Sequence 0 Digital Comparator Select (ADCSSDC0), offset 0x054

This register determines which digital comparator receives the sample from the given conversion on Sample Sequence 0, if the corresponding SnDCOP bit in the **ADCSSOP0** register is set.

ADC Sample Sequence 0 Digital Comparator Select (ADCSSDC0)

ADC0 base: 0x4003.8000 ADC1 base: 0x4003.9000 Offset 0x054


15:12

S3DCSEL

R/W

0x0

Type R/W, reset 0x0000.0000



Bit/Field	Name	Type	Reset	Description
31:28	S7DCSEL	R/W	0x0	Sample 7 Digital Comparator Select

When the S7DCOP bit in the **ADCSSOP0** register is set, this field indicates which digital comparator unit (and its associated set of control registers) receives the eighth sample from Sample Sequencer 0.

Note: Values not listed are reserved.

				Value I	Description
				0x0 I	Digital Comparator Unit 0 (ADCDCCMP0 and ADCDCCTL0)
				0x1 I	Digital Comparator Unit 1 (ADCDCCMP1 and ADCDCCTL1)
				0x2 I	Digital Comparator Unit 2 (ADCDCCMP2 and ADCDCCTL2)
				0x3 I	Digital Comparator Unit 3 (ADCDCCMP3 and ADCDCCTL3)
				0x4 I	Digital Comparator Unit 4 (ADCDCCMP4 and ADCDCCTL4)
				0x5 I	Digital Comparator Unit 5 (ADCDCCMP5 and ADCDCCTL5)
				0x6 I	Digital Comparator Unit 6 (ADCDCCMP6 and ADCDCCTL6)
				0x7 I	Digital Comparator Unit 7 (ADCDCCMP7 and ADCDCCTL7)
27:24	S6DCSEL	R/W	0x0	Sample	6 Digital Comparator Select
					d has the same encodings as S7DCSEL but is used during the sample.
23:20	S5DCSEL	R/W	0x0	Sample	5 Digital Comparator Select
				This field sixth sai	d has the same encodings as ${\tt S7DCSEL}$ but is used during the mple.
19:16	S4DCSEL	R/W	0x0	Sample	4 Digital Comparator Select
				This fiel	d has the same encodings as S7DCSEL but is used during the

fifth sample.

fourth sample.

Sample 3 Digital Comparator Select

This field has the same encodings as STDCSEL but is used during the

Bit/Field	Name	Type	Reset	Description
11:8	S2DCSEL	R/W	0x0	Sample 2 Digital Comparator Select This field has the same encodings as S7DCSEL but is used during the third sample.
7:4	S1DCSEL	R/W	0x0	Sample 1 Digital Comparator Select This field has the same encodings as S7DCSEL but is used during the second sample.
3:0	SODCSEL	R/W	0x0	Sample 0 Digital Comparator Select This field has the same encodings as S7DCSEL but is used during the first sample.

Register 27: ADC Sample Sequence Extended Input Multiplexer Select 0 (ADCSSEMUX0), offset 0x058

This register, along with the **ADCSSMUX0** register, defines the analog input configuration for each sample in a sequence executed with Sample Sequencer 0. If a bit in this register is set, the corresponding MUXn field in the **ADCSSMUX0** register selects from AIN[21:16]. When a bit in this register is clear, the corresponding MUXn field selects from AIN[15:0]. This register is 32 bits wide and contains information for eight possible samples.

Note that this register is not used when the differential channel designation is used (the Dn bit is set in the ADCSSCTL0 register) because the ADCSSMUX0 register can select all the available pairs.

ADC Sample Sequence Extended Input Multiplexer Select 0 (ADCSSEMUX0)

ADC0 base: 0x4003.8000 ADC1 base: 0x4003.9000 Offset 0x058 Type R/W, reset 0x0000.0000

23:21

30

		reserved		EMUX7		reserved		EMUX6		reserved		EMUX5		reserved		EMUX4
Type Reset	RO 0	RO 0	RO 0	R/W 0	RO 0	RO 0	RO 0	R/W 0	RO 0	RO 0	RO 0	R/W 0	RO 0	RO 0	RO 0	R/W 0
_	15	14	13	12	11	10	9	8	7	6	5	4	3	2	1	0
		reserved		EMUX3		reserved		EMUX2		reserved		EMUX1		reserved		EMUX0
Type Reset	RO 0	RO 0	RO 0	R/W 0	RO 0	RO 0	RO 0	R/W 0	RO 0	RO 0	RO 0	R/W 0	RO 0	RO 0	RO 0	R/W 0
E	sit/Field		Nam	ie	Ту	ре	Reset	Des	cription							
	31:29		reserv	/ed	R	0	0x0	com	patibility		re prod	ucts, the	value of	erved bit. f a reserve on.	•	
	28		EMU.	X7	R	W	0x0	8th	Sample	Input Sele	ect (Upp	oer Bit)				
										field is use th the san			hth sar	nple of a s	equenc	ce
								Valu	ue Des	cription						
								0	ADC	•	registe			om AIN[15		•
								1	the A		JX0 reg			om AIN[2 e, if the MU		
	27:25		reserv	ved	R	0	0x0	com	patibility		re prod	ucts, the	value of	erved bit. f a reserve		
	24		EMU	X6	R	W	0x0	7th	Sample	Input Sele	ect (Upp	per Bit)				
								exec				•		ample of a has the sa		

Software should not rely on the value of a reserved bit. To provide

preserved across a read-modify-write operation.

compatibility with future products, the value of a reserved bit should be

RO

reserved

0x0

Bit/Field	Name	Туре	Reset	Description
20	EMUX5	R/W	0x0	6th Sample Input Select (Upper Bit)
				The EMUX5 field is used during the sixth sample of a sequence executed with the sample sequencer. This bit has the same description as EMUX7.
19:17	reserved	RO	0x0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
16	EMUX4	R/W	0x0	5th Sample Input Select (Upper Bit)
				The ${\tt EMUX4}$ field is used during the fifth sample of a sequence executed with the sample sequencer. This bit has the same description as ${\tt EMUX7}$.
15:13	reserved	RO	0x0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
12	EMUX3	R/W	0x0	4th Sample Input Select (Upper Bit)
				The EMUX3 field is used during the fourth sample of a sequence executed with the sample sequencer. This bit has the same description as EMUX7.
11:9	reserved	RO	0x0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
8	EMUX2	R/W	0x0	3rd Sample Input Select (Upper Bit)
				The ${\tt EMUX2}$ field is used during the third sample of a sequence executed with the sample sequencer. This bit has the same description as ${\tt EMUX7}$.
7:5	reserved	RO	0x0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
4	EMUX1	R/W	0x0	2th Sample Input Select (Upper Bit)
				The EMUX1 field is used during the second sample of a sequence executed with the sample sequencer. This bit has the same description as EMUX7.
3:1	reserved	RO	0x0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
0	EMUX0	R/W	0x0	1st Sample Input Select (Upper Bit)
				The EMUX0 field is used during the first sample of a sequence executed with the sample sequencer. This bit has the same description as EMUX7.

Register 28: ADC Sample Sequence Input Multiplexer Select 1 (ADCSSMUX1), offset 0x060

Register 29: ADC Sample Sequence Input Multiplexer Select 2 (ADCSSMUX2), offset 0x080


This register, along with the **ADCSSEMUX1** or **ADCSSEMUX2** register, defines the analog input configuration for each sample in a sequence executed with Sample Sequencer 1 or 2. If the corresponding EMUXn bit in the **ADCSSEMUX1** or **ADCSSEMUX2** register is set, the MUXn field in this register selects from AIN[21:16]. When the corresponding EMUXn bit is clear, the MUXn field selects from AIN[15:0]. These registers are 16 bits wide and contain information for four possible samples. See the **ADCSSMUX0** register on page 851 for detailed bit descriptions. The **ADCSSMUX1** register affects Sample Sequencer 1 and the **ADCSSMUX2** register affects Sample Sequencer 2.

Note: Channels AIN[31:22] do not exist on this microcontroller. Configuring MUXn to be 0xA-0xF when the corresponding EMUXn bit is set results in undefined behavior.

ADC Sample Sequence Input Multiplexer Select n (ADCSSMUXn)

ADC0 base: 0x4003.8000 ADC1 base: 0x4003.9000 Offset 0x060

Type R/W, reset 0x0000.0000



Bit/Field	Name	Type	Reset	Description
31:16	reserved	RO	0x0000	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
15:12	MUX3	R/W	0x0	4th Sample Input Select
11:8	MUX2	R/W	0x0	3rd Sample Input Select
7:4	MUX1	R/W	0x0	2nd Sample Input Select
3:0	MUX0	R/W	0x0	1st Sample Input Select

Register 30: ADC Sample Sequence Control 1 (ADCSSCTL1), offset 0x064 Register 31: ADC Sample Sequence Control 2 (ADCSSCTL2), offset 0x084

These registers contain the configuration information for each sample for a sequence executed with Sample Sequencer 1 or 2. When configuring a sample sequence, the END bit must be set for the final sample, whether it be after the first sample, fourth sample, or any sample in between. These registers are 16-bits wide and contain information for four possible samples. See the **ADCSSCTL0** register on page 853 for detailed bit descriptions. The **ADCSSCTL1** register configures Sample Sequencer 1 and the **ADCSSCTL2** register configures Sample Sequencer 2.

ADC Sample Sequence Control n (ADCSSCTLn)

ADC0 base: 0x4003.8000 ADC1 base: 0x4003.9000 Offset 0x064

Type R/W, reset 0x0000.0000

	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16
ĺ		1			1			rese	rved •		1					
Туре	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO
Reset	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0
_	15	14	13	12	11	10	9	8	7	6	5	4	3	2	1	0
	TS3	IE3	END3	D3	TS2	IE2	END2	D2	TS1	IE1	END1	D1	TS0	IE0	END0	D0
Туре	R/W	R/W	R/W	R/W	R/W	R/W	R/W	R/W	R/W	R/W	R/W	R/W	R/W	R/W	R/W	R/W
Reset	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0

Bit/Field	Name	Туре	Reset	Description
31:16	reserved	RO	0x0000	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
15	TS3	R/W	0	4th Sample Temp Sensor Select
				Value Description
				The input pin specified by the ADCSSMUXn register is read during the fourth sample of the sample sequence.
				1 The temperature sensor is read during the fourth sample of the sample sequence.
14	IE3	R/W	0	4th Sample Interrupt Enable

Value Description

- The raw interrupt is not asserted to the interrupt controller.
- The raw interrupt signal (INR0 bit) is asserted at the end of the fourth sample's conversion. If the MASK0 bit in the ADCIM register is set, the interrupt is promoted to the interrupt controller.

It is legal to have multiple samples within a sequence generate interrupts.

Bit/Field	Name	Туре	Reset	Description
13	END3	R/W	0	4th Sample is End of Sequence
				Value Description
				O Another sample in the sequence is the final sample.
				1 The fourth sample is the last sample of the sequence.
				It is possible to end the sequence on any sample position. Software must set an ENDn bit somewhere within the sequence. Samples defined after the sample containing a set ENDn bit are not requested for conversion even though the fields may be non-zero.
12	D3	R/W	0	4th Sample Differential Input Select
				Value Description
				0 The analog inputs are not differentially sampled.
				The analog input is differentially sampled. The corresponding ADCSSMUXn nibble must be set to the pair number "i", where the paired inputs are "2i and 2i+1".
				Because the temperature sensor does not have a differential option, this bit must not be set when the ${\tt TS3}$ bit is set.
11	TS2	R/W	0	3rd Sample Temp Sensor Select
				Value Description
				The input pin specified by the ADCSSMUXn register is read during the third sample of the sample sequence.
				1 The temperature sensor is read during the third sample of the sample sequence.
10	IE2	R/W	0	3rd Sample Interrupt Enable
				Value Description
				The raw interrupt is not asserted to the interrupt controller.
				The raw interrupt signal (INR0 bit) is asserted at the end of the third sample's conversion. If the MASK0 bit in the ADCIM register is set, the interrupt is promoted to the interrupt controller.
				It is legal to have multiple samples within a sequence generate interrupts.
9	END2	R/W	0	3rd Sample is End of Sequence
				Value Description
				O Another sample in the sequence is the final sample.
				1 The third sample is the last sample of the sequence.
				It is possible to end the sequence on any sample position. Software must set an \mathtt{ENDn} bit somewhere within the sequence. Samples defined after the sample containing a set \mathtt{ENDn} bit are not requested for conversion even though the fields may be non-zero.

February 20, 2013 871

Bit/Field	Name	Туре	Reset	Description
8	D2	R/W	0	3rd Sample Differential Input Select
				Value Description
				O The analog inputs are not differentially sampled.
				The analog input is differentially sampled. The corresponding ADCSSMUXn nibble must be set to the pair number "i", where the paired inputs are "2i and 2i+1".
				Because the temperature sensor does not have a differential option, this bit must not be set when the ${\tt TS2}$ bit is set.
7	TS1	R/W	0	2nd Sample Temp Sensor Select
				Value Description
				The input pin specified by the ADCSSMUXn register is read during the second sample of the sample sequence.
				1 The temperature sensor is read during the second sample of the sample sequence.
6	IE1	R/W	0	2nd Sample Interrupt Enable
				Value Description
				The raw interrupt is not asserted to the interrupt controller.
				The raw interrupt signal (INR0 bit) is asserted at the end of the second sample's conversion. If the MASK0 bit in the ADCIM register is set, the interrupt is promoted to the interrupt controller.
				It is legal to have multiple samples within a sequence generate interrupts.
5	END1	R/W	0	2nd Sample is End of Sequence
				Value Description
				O Another sample in the sequence is the final sample.
				1 The second sample is the last sample of the sequence.
				It is possible to end the sequence on any sample position. Software must set an \mathtt{ENDn} bit somewhere within the sequence. Samples defined after the sample containing a set \mathtt{ENDn} bit are not requested for conversion even though the fields may be non-zero.
4	D1	R/W	0	2nd Sample Differential Input Select
				Value Description
				The analog inputs are not differentially sampled.
				The analog input is differentially sampled. The corresponding ADCSSMUXn nibble must be set to the pair number "i", where the paired inputs are "2i and 2i+1".
				Because the temperature sensor does not have a differential option, this bit must not be set when the TS1 bit is set.

872 February 20, 2013

Bit/Field	Name	Туре	Reset	Description
3	TS0	R/W	0	1st Sample Temp Sensor Select
				Value Description The input pin specified by the ADCSSMUXn register is read during the first sample of the sample sequence.
				1 The temperature sensor is read during the first sample of the sample sequence.
2	IE0	R/W	0	1st Sample Interrupt Enable
				Value Description
				O The raw interrupt is not asserted to the interrupt controller.
				The raw interrupt signal (INRO bit) is asserted at the end of the first sample's conversion. If the MASKO bit in the ADCIM register is set, the interrupt is promoted to the interrupt controller.
				It is legal to have multiple samples within a sequence generate interrupts.
1	END0	R/W	0	1st Sample is End of Sequence
				Value Description
				O Another sample in the sequence is the final sample.
				1 The first sample is the last sample of the sequence.
				It is possible to end the sequence on any sample position. Software must set an ${\tt ENDn}$ bit somewhere within the sequence. Samples defined after the sample containing a set ${\tt ENDn}$ bit are not requested for conversion even though the fields may be non-zero.
0	D0	R/W	0	1st Sample Differential Input Select
				Value Description
				0 The analog inputs are not differentially sampled.
				The analog input is differentially sampled. The corresponding ADCSSMUXn nibble must be set to the pair number "i", where the paired inputs are "2i and 2i+1".
				Because the temperature sensor does not have a differential option, this bit must not be set when the ${\tt TS0}$ bit is set.

February 20, 2013 873

Register 32: ADC Sample Sequence 1 Operation (ADCSSOP1), offset 0x070 Register 33: ADC Sample Sequence 2 Operation (ADCSSOP2), offset 0x090


This register determines whether the sample from the given conversion on Sample Sequence n is saved in the Sample Sequence n FIFO or sent to the digital comparator unit. The **ADCSSOP1** register controls Sample Sequencer 1 and the **ADCSSOP2** register controls Sample Sequencer 2.

ADC Sample Sequence n Operation (ADCSSOPn)

ADC0 base: 0x4003.8000 ADC1 base: 0x4003.9000

Offset 0x070

Type R/W, reset 0x0000.0000



Same definition as S3DCOP but used during the first sample.

Register 34: ADC Sample Sequence 1 Digital Comparator Select (ADCSSDC1), offset 0x074

Register 35: ADC Sample Sequence 2 Digital Comparator Select (ADCSSDC2), offset 0x094

These registers determine which digital comparator receives the sample from the given conversion on Sample Sequence n if the corresponding SnDCOP bit in the **ADCSSOPn** register is set. The **ADCSSDC1** register controls the selection for Sample Sequencer 1 and the **ADCSSDC2** register controls the selection for Sample Sequencer 2.

ADC Sample Sequence n Digital Comparator Select (ADCSSDCn)

N I = ---

ADC0 base: 0x4003.8000 ADC1 base: 0x4003.9000 Offset 0x074

D:4/E:414

11:8

Type R/W, reset 0x0000.0000

	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16
								rese	rved							
Type	RO															
Reset	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0
	15	14	13	12	11	10	9	8	7	6	5	4	3	2	1	0
		S3D0	CSEL	•		S2D0	CSEL	1	'	S1D0	CSEL		'	SODO	SEL	'
Type Reset	R/W 0															

Bit/Field	Name	туре	Reset	Description
31:16	reserved	RO	0x0000	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
15:12	S3DCSEL	R/W	0x0	Sample 3 Digital Comparator Select

D = = ==i=+i==

When the S3DCOP bit in the **ADCSSOPn** register is set, this field indicates which digital comparator unit (and its associated set of control registers) receives the eighth sample from Sample Sequencer n.

Note: Values not listed are reserved.

Value Description Digital Comparator Unit 0 (ADCDCCMP0 and ADCCCTL0) 0x0 Digital Comparator Unit 1 (ADCDCCMP1 and ADCCCTL1) 0x1 0x2 Digital Comparator Unit 2 (ADCDCCMP2 and ADCCCTL2) 0x3 Digital Comparator Unit 3 (ADCDCCMP3 and ADCCCTL3) Digital Comparator Unit 4 (ADCDCCMP4 and ADCCCTL4) 0x4 0x5 Digital Comparator Unit 5 (ADCDCCMP5 and ADCCCTL5) 0x6 Digital Comparator Unit 6 (ADCDCCMP6 and ADCCCTL6) Digital Comparator Unit 7 (ADCDCCMP7 and ADCCCTL7)

S2DCSEL R/W 0x0 Sample 2 Digital Comparator Select

This field has the same encodings as ${\tt S3DCSEL}$ but is used during the third sample.

Bit/Field	Name	Type	Reset	Description
7:4	S1DCSEL	R/W	0x0	Sample 1 Digital Comparator Select This field has the same encodings as S3DCSEL but is used during the second sample.
3:0	SODCSEL	R/W	0x0	Sample 0 Digital Comparator Select This field has the same encodings as S3DCSEL but is used during the first sample.

Register 36: ADC Sample Sequence Extended Input Multiplexer Select 1 (ADCSSEMUX1), offset 0x078

Register 37: ADC Sample Sequence Extended Input Multiplexer Select 2 (ADCSSEMUX2), offset 0x098

This register, along with the ADCSSMUX1 or ADCSSMUX2 register, defines the analog input configuration for each sample in a sequence executed with either Sample Sequencer 1 or 2. If a bit in this register is set, the corresponding MUXn field in the ADCSSMUX1 or ADCSSMUX2 register selects from AIN[21:16]. When a bit in this register is clear, the corresponding MUXn field selects from AIN[15:0]. This register is 16 bits wide and contains information for four possible samples. The ADCSSEMUX1 register controls Sample Sequencer 1 and the ADCSSEMUX2 register controls Sample Sequencer 2.

Note that this register is not used when the differential channel designation is used (the Dn bit is set in the ADCSSCTL1 or ADCSSCTL2 register) because the ADCSSMUX1 or ADCSSMUX2 register can select all the available pairs.

ADC Sample Sequence Extended Input Multiplexer Select n (ADCSSEMUXn)

Type

RO

Reset

0x0


ADC0 base: 0x4003.8000 ADC1 base: 0x4003.9000 Offset 0x078

Bit/Field

11:9

Name

reserved



31:13	reserved	RO	0x0000	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
12	EMUX3	R/W	0x0	4th Sample Input Select (Upper Bit)
				The EMUX3 field is used during the fourth sample of a sequence executed

Description

Value Description

with the sample sequencer.

- The fourth sample input is selected from AIN[15:0] using the ADCSSMUX1 or ADCSSMUX2 register. For example, if the MUX3 field is 0x0, AIN0 is selected.
- The fourth sample input is selected from AIN[21:16] using the **ADCSSMUX1** or **ADCSSMUX2** register. For example, if the MUX3 field is 0x0, AIN16 is selected.

Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.

Bit/Field	Name	Туре	Reset	Description
8	EMUX2	R/W	0x0	3rd Sample Input Select (Upper Bit) The ${\tt EMUX2}$ field is used during the third sample of a sequence executed with the sample sequencer. This bit has the same description as ${\tt EMUX3}$.
7:5	reserved	RO	0x0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
4	EMUX1	R/W	0x0	2th Sample Input Select (Upper Bit) The EMUX1 field is used during the second sample of a sequence executed with the sample sequencer. This bit has the same description as EMUX3.
3:1	reserved	RO	0x0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
0	EMUX0	R/W	0x0	1st Sample Input Select (Upper Bit) The EMUX0 field is used during the first sample of a sequence executed with the sample sequencer. This bit has the same description as EMUX3.


Register 38: ADC Sample Sequence Input Multiplexer Select 3 (ADCSSMUX3), offset 0x0A0

This register, along with the **ADCSSEMUX3** register, defines the analog input configuration for the sample in a sequence executed with Sample Sequencer 3. If the EMUX0 bit in the **ADCSSEMUX3** register is set, the MUX0 field in this register selects from AIN[21:16]. When the EMUX0 bit is clear, the MUX0 field selects from AIN[15:0]. This register is four bits wide and contains information for one possible sample. See the **ADCSSMUX0** register on page 851 for detailed bit descriptions.

ADC Sample Sequence Input Multiplexer Select 3 (ADCSSMUX3)

ADC0 base: 0x4003.8000 ADC1 base: 0x4003.9000 Offset 0x0A0

Type R/W, reset 0x0000.0000




Bit/Field	Name	Type	Reset	Description
31:4	reserved	RO	0x0000.000	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
3:0	MUX0	R/W	0	1st Sample Input Select

Register 39: ADC Sample Sequence Control 3 (ADCSSCTL3), offset 0x0A4

This register contains the configuration information for a sample executed with Sample Sequencer 3. When configuring a sample sequence in this register, the END bit must be set for this sample. This register is 4 bits wide and contains information for one possible sample. See the **ADCSSCTL0** register on page 853 for detailed bit descriptions.

ADC Sample Sequence Control 3 (ADCSSCTL3)

ADC0 base: 0x4003.8000 ADC1 base: 0x4003.9000 Offset 0x0A4 Type R/W, reset 0x0000.0000



Bit/Field	Name	Туре	Reset	Description
31:4	reserved	RO	0x0000.000	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
3	TS0	R/W	0	1st Sample Temp Sensor Select
				Value Description
				The input pin specified by the ADCSSMUXn register is read during the first sample of the sample sequence.
				1 The temperature sensor is read during the first sample of the sample sequence.
2	IE0	R/W	0	Sample Interrupt Enable
				Value Description
				O The raw interrupt is not asserted to the interrupt controller.
				The raw interrupt signal (INR0 bit) is asserted at the end of this sample's conversion. If the MASK0 bit in the ADCIM register is set, the interrupt is promoted to the interrupt controller.
				It is legal to have multiple samples within a sequence generate interrupts.
1	END0	R/W	0	End of Sequence
				This bit must be set before initiating single sample sequence.
				Value Description

0

1

Sampling and conversion continues.

This is the end of sequence.

Bit/Field	Name	Туре	Reset	Description
0	D0	R/W	0	Sample Differential Input Select
				Value Description
				0 The analog inputs are not differentially sampled.
				The analog input is differentially sampled. The corresponding ADCSSMUXn nibble must be set to the pair number "i", where the paired inputs are "2i and 2i+1".

Because the temperature sensor does not have a differential option, this bit must not be set when the ${\tt TS0}$ bit is set.

Register 40: ADC Sample Sequence 3 Operation (ADCSSOP3), offset 0x0B0


This register determines whether the sample from the given conversion on Sample Sequence 3 is saved in the Sample Sequence 3 FIFO or sent to the digital comparator unit.

ADC Sample Sequence 3 Operation (ADCSSOP3)

ADC0 base: 0x4003.8000 ADC1 base: 0x4003.9000

Offset 0x0B0

Type R/W, reset 0x0000.0000



Bit/Field	Name	Type	Reset	Description
31:1	reserved	RO	0x0000.000	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
0	SODCOP	R/W	0	Sample 0 Digital Comparator Operation

Value Description


- 0 The sample is saved in Sample Sequence FIFO3.
- The sample is sent to the digital comparator unit specified by the SODCSEL bit in the ADCSSDC03 register, and the value is not written to the FIFO.

Register 41: ADC Sample Sequence 3 Digital Comparator Select (ADCSSDC3), offset 0x0B4

This register determines which digital comparator receives the sample from the given conversion on Sample Sequence 3 if the corresponding SnDCOP bit in the **ADCSSOP3** register is set.

ADC Sample Sequence 3 Digital Comparator Select (ADCSSDC3)

ADC0 base: 0x4003.8000 ADC1 base: 0x4003.9000 Offset 0x0B4



Bit/Field	Name	Type	Reset	Description
31:4	reserved	RO	0x0000.000	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
3:0	SODCSEL	R/W	0x0	Sample 0 Digital Comparator Select

When the SODCOP bit in the **ADCSSOP3** register is set, this field indicates which digital comparator unit (and its associated set of control registers) receives the sample from Sample Sequencer 3.

Note: Values not listed are reserved.

Value Description	
0x0 Digital Comparator Unit 0 (ADCDCCMP0 and ADCCCTL	.0)
0x1 Digital Comparator Unit 1 (ADCDCCMP1 and ADCCCTL	.1)
0x2 Digital Comparator Unit 2 (ADCDCCMP2 and ADCCCTL	.2)
0x3 Digital Comparator Unit 3 (ADCDCCMP3 and ADCCCTL	3)
0x4 Digital Comparator Unit 4 (ADCDCCMP4 and ADCCCTL	4)
0x5 Digital Comparator Unit 5 (ADCDCCMP5 and ADCCCTL	5)
0x6 Digital Comparator Unit 6 (ADCDCCMP6 and ADCCCTL	.6)
0x7 Digital Comparator Unit 7 (ADCDCCMP7 and ADCCCTL	.7)

Register 42: ADC Sample Sequence Extended Input Multiplexer Select 3 (ADCSSEMUX3), offset 0x0B8


This register, along with the **ADCSSMUX3** register, defines the analog input configuration for the sample in a sequence executed with Sample Sequencer 3. If EMUX0 is set, the MUX0 field in the **ADCSSMUX3** register selects from AIN[21:16]. When EMUX0 is clear, the MUX0 field selects from AIN[15:0]. This register is 1 bit wide and contains information for one possible sample.

Note that this register is not used when the differential channel designation is used (the Dn bit is set in the ADCSSCTL3 register) because the ADCSSMUX3 register can select all the available pairs.

ADC Sample Sequence Extended Input Multiplexer Select 3 (ADCSSEMUX3)

ADC0 base: 0x4003.8000 ADC1 base: 0x4003.9000 Offset 0x0B8

Type R/W, reset 0x0000.0000



Bit/Field	Name	Type	Reset	Description
31:1	reserved	RO	0x0000.000	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
0	EMUX0	R/W	0x0	1st Sample Input Select (Upper Bit)
				The EMELY 0 field is used during the only comple of a coguence executed

The ${\tt EMUX0}$ field is used during the only sample of a sequence executed with the sample sequencer.

Value Description

- The sample input is selected from AIN[15:0] using the ADCSSMUX3 register. For example, if the MUX0 field is 0x0, AIN0 is selected.
- The sample input is selected from AIN[21:16] using the ADCSSMUX3 register. For example, if the MUX0 field is 0x0, AIN16 is selected.


Register 43: ADC Digital Comparator Reset Initial Conditions (ADCDCRIC), offset 0xD00

This register provides the ability to reset any of the digital comparator interrupt or trigger functions back to their initial conditions. Resetting these functions ensures that the data that is being used by the interrupt and trigger functions in the digital comparator unit is not stale.

ADC Digital Comparator Reset Initial Conditions (ADCDCRIC)

ADC0 base: 0x4003.8000 ADC1 base: 0x4003.9000 Offset 0xD00

Type WO, reset 0x0000.0000



Bit/Field	Name	Туре	Reset	Description
31:24	reserved	RO	0x00	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
23	DCTRIG7	WO	0	Digital Comparator Trigger 7

Value Description

0 No effect.

1 Resets the Digital Comparator 7 trigger unit to its initial conditions.

When the trigger has been cleared, this bit is automatically cleared.

Because the digital comparators use the current and previous ADC conversion values to determine when to assert the trigger, it is important to reset the digital comparator to initial conditions when starting a new sequence so that stale data is not used. After setting this bit, software should wait until the bit clears before continuing.

22 DCTRIG6 WO 0

Digital Comparator Trigger 6

Value Description

0 No effect.

Resets the Digital Comparator 6 trigger unit to its initial conditions.

When the trigger has been cleared, this bit is automatically cleared.

Because the digital comparators use the current and previous ADC conversion values to determine when to assert the trigger, it is important to reset the digital comparator to initial conditions when starting a new sequence so that stale data is not used.

Bit/Field	Name	Туре	Reset	Description
21	DCTRIG5	WO	0	Digital Comparator Trigger 5
				Value Description
				0 No effect.
				 Resets the Digital Comparator 5 trigger unit to its initial conditions.
				When the trigger has been cleared, this bit is automatically cleared.
				Because the digital comparators use the current and previous ADC conversion values to determine when to assert the trigger, it is important to reset the digital comparator to initial conditions when starting a new sequence so that stale data is not used.
20	DCTRIG4	WO	0	Digital Comparator Trigger 4
				Value Description
				0 No effect.
				 Resets the Digital Comparator 4 trigger unit to its initial conditions.
				When the trigger has been cleared, this bit is automatically cleared.
				Because the digital comparators use the current and previous ADC conversion values to determine when to assert the trigger, it is important to reset the digital comparator to initial conditions when starting a new sequence so that stale data is not used.
19	DCTRIG3	WO	0	Digital Comparator Trigger 3
				Value Description
				0 No effect.
				1 Resets the Digital Comparator 3 trigger unit to its initial conditions.
				When the trigger has been cleared, this bit is automatically cleared.
				Because the digital comparators use the current and previous ADC conversion values to determine when to assert the trigger, it is important to reset the digital comparator to initial conditions when starting a new sequence so that stale data is not used.
18	DCTRIG2	WO	0	Digital Comparator Trigger 2
				Value Description
				0 No effect.
				 Resets the Digital Comparator 2 trigger unit to its initial conditions.
				When the trigger has been cleared, this bit is automatically cleared.

886 February 20, 2013

Because the digital comparators use the current and previous ADC conversion values to determine when to assert the trigger, it is important to reset the digital comparator to initial conditions when starting a new

sequence so that stale data is not used.

Bit/Field	Name	Туре	Reset	Description
17	DCTRIG1	WO	0	Digital Comparator Trigger 1
				Value Description
				0 No effect.
				1 Resets the Digital Comparator 1 trigger unit to its initial conditions.
				When the trigger has been cleared, this bit is automatically cleared.
				Because the digital comparators use the current and previous ADC conversion values to determine when to assert the trigger, it is important to reset the digital comparator to initial conditions when starting a new sequence so that stale data is not used.
16	DCTRIG0	WO	0	Digital Comparator Trigger 0
				Value Description
				0 No effect.
				1 Resets the Digital Comparator 0 trigger unit to its initial conditions.
				When the trigger has been cleared, this bit is automatically cleared.
				Because the digital comparators use the current and previous ADC conversion values to determine when to assert the trigger, it is important to reset the digital comparator to initial conditions when starting a new sequence so that stale data is not used.
15:8	reserved	RO	0x00	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
7	DCINT7	WO	0	Digital Comparator Interrupt 7
				Value Description
				0 No effect.
				1 Resets the Digital Comparator 7 interrupt unit to its initial conditions.
				When the interrupt has been cleared, this bit is automatically cleared.
				Because the digital comparators use the current and previous ADC conversion values to determine when to assert the interrupt, it is important to reset the digital comparator to initial conditions when starting a new sequence so that stale data is not used.
6	DCINT6	WO	0	Digital Comparator Interrupt 6
				Value Description
				0 No effect.
				1 Resets the Digital Comparator 6 interrupt unit to its initial conditions.
				When the interrupt has been cleared, this bit is automatically cleared.
				Because the digital comparators use the current and previous ADC conversion values to determine when to assert the interrupt, it is important to reset the digital comparator to initial conditions when starting a new sequence so that stale data is not used.

February 20, 2013 887

Bit/Field	Name	Туре	Reset	Description
5	DCINT5	WO	0	Digital Comparator Interrupt 5
				Value Description
				0 No effect.
				1 Resets the Digital Comparator 5 interrupt unit to its initial conditions.
				When the interrupt has been cleared, this bit is automatically cleared.
				Because the digital comparators use the current and previous ADC conversion values to determine when to assert the interrupt, it is important to reset the digital comparator to initial conditions when starting a new sequence so that stale data is not used.
4	DCINT4	WO	0	Digital Comparator Interrupt 4
				Value Description
				0 No effect.
				1 Resets the Digital Comparator 4 interrupt unit to its initial conditions.
				When the interrupt has been cleared, this bit is automatically cleared.
				Because the digital comparators use the current and previous ADC conversion values to determine when to assert the interrupt, it is important to reset the digital comparator to initial conditions when starting a new sequence so that stale data is not used.
3	DCINT3	WO	0	Digital Comparator Interrupt 3
				Value Description
				0 No effect.
				1 Resets the Digital Comparator 3 interrupt unit to its initial conditions.
				When the interrupt has been cleared, this bit is automatically cleared.
				Because the digital comparators use the current and previous ADC conversion values to determine when to assert the interrupt, it is important to reset the digital comparator to initial conditions when starting a new sequence so that stale data is not used.
2	DCINT2	WO	0	Digital Comparator Interrupt 2
				Value Description
				0 No effect.
				1 Resets the Digital Comparator 2 interrupt unit to its initial conditions.
				When the interrupt has been cleared, this bit is automatically cleared.
				Because the digital comparators use the current and previous ADC

888 February 20, 2013

conversion values to determine when to assert the interrupt, it is important to reset the digital comparator to initial conditions when starting

a new sequence so that stale data is not used.

Bit/Field	Name	Туре	Reset	Description
1	DCINT1	WO	0	Digital Comparator Interrupt 1
				Value Description
				0 No effect.
				1 Resets the Digital Comparator 1 interrupt unit to its initial conditions.
				When the interrupt has been cleared, this bit is automatically cleared.
				Because the digital comparators use the current and previous ADC conversion values to determine when to assert the interrupt, it is important to reset the digital comparator to initial conditions when starting a new sequence so that stale data is not used.
0	DCINT0	WO	0	Digital Comparator Interrupt 0
				Value Description
				0 No effect.
				 Resets the Digital Comparator 0 interrupt unit to its initial conditions.


When the interrupt has been cleared, this bit is automatically cleared. Because the digital comparators use the current and previous ADC conversion values to determine when to assert the interrupt, it is important to reset the digital comparator to initial conditions when starting a new sequence so that stale data is not used.

Register 44: ADC Digital Comparator Control 0 (ADCDCCTL0), offset 0xE00 Register 45: ADC Digital Comparator Control 1 (ADCDCCTL1), offset 0xE04 Register 46: ADC Digital Comparator Control 2 (ADCDCCTL2), offset 0xE08 Register 47: ADC Digital Comparator Control 3 (ADCDCCTL3), offset 0xE0C Register 48: ADC Digital Comparator Control 4 (ADCDCCTL4), offset 0xE10 Register 49: ADC Digital Comparator Control 5 (ADCDCCTL5), offset 0xE14 Register 50: ADC Digital Comparator Control 6 (ADCDCCTL6), offset 0xE18 Register 51: ADC Digital Comparator Control 7 (ADCDCCTL7), offset 0xE1C

This register provides the comparison encodings that generate an interrupt and/or PWM trigger. See "Interrupt/ADC-Trigger Selector" on page 1242 for more information on using the ADC digital comparators to trigger a PWM generator.

ADC Digital Comparator Control n (ADCDCCTLn)

ADC0 base: 0x4003.8000 ADC1 base: 0x4003.9000 Offset 0xE00



Bit/Field	Name	Type	Reset	Description
31:13	reserved	RO	0x0000.0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
12	CTE	R/W	0	Comparison Trigger Enable

Value Description

- 0 Disables the trigger function state machine. ADC conversion data is ignored by the trigger function.
- 1 Enables the trigger function state machine. The ADC conversion data is used to determine if a trigger should be generated according to the programming of the CTC and CTM fields.

Bit/Field	Name	Туре	Reset	Description
11:10	CTC	R/W	0x0	Comparison Trigger Condition
				This field specifies the operational region in which a trigger is generated when the ADC conversion data is compared against the values of COMPO and COMP1. The COMPO and COMP1 fields are defined in the ADCDCCMPx registers.
				Value Description
				0x0 Low Band
				ADC Data < COMP0 ≤ COMP1
				0x1 Mid Band
				COMP0 < ADC Data ≤ COMP1
				0x2 reserved
				0x3 High Band
				COMP0 ≤ COMP1 ≤ ADC Data
9:8	СТМ	R/W	0x0	Comparison Trigger Mode
				This field specifies the mode by which the trigger comparison is made.
				Value Description
				0x0 Always
				This mode generates a trigger every time the ADC conversion data falls within the selected operational region.
				0x1 Once
				This mode generates a trigger the first time that the ADC conversion data enters the selected operational region.
				0x2 Hysteresis Always
				This mode generates a trigger when the ADC conversion data falls within the selected operational region and continues to generate the trigger until the hysteresis condition is cleared by entering the opposite operational region.
				Note that the hysteresis modes are only defined for CTC encodings of 0x0 and 0x3.
				0x3 Hysteresis Once
				This mode generates a trigger the first time that the ADC conversion data falls within the selected operational region. No additional triggers are generated until the hysteresis condition is cleared by entering the opposite operational region.
				Note that the hysteresis modes are only defined for ${\tt CTC}$ encodings of 0x0 and 0x3.
7:5	reserved	RO	0x0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.

Bit/Field	Name	Туре	Reset	Description
4	CIE	R/W	0	Comparison Interrupt Enable
				Value Description
				0 Disables the comparison interrupt. ADC conversion data has no effect on interrupt generation.
				Enables the comparison interrupt. The ADC conversion data is used to determine if an interrupt should be generated according to the programming of the CIC and CIM fields.
3:2	CIC	R/W	0x0	Comparison Interrupt Condition
				This field specifies the operational region in which an interrupt is generated when the ADC conversion data is compared against the values of COMPO and COMP1. The COMPO and COMP1 fields are defined in the ADCDCCMPx registers.
				Value Description
				0x0 Low Band
				ADC Data < COMP0 ≤ COMP1
				0x1 Mid Band
				COMP0 ≤ ADC Data < COMP1
				0x2 reserved
				0x3 High Band COMP0 < COMP1 ≤ ADC Data
				COME O VEORE I TABO BUILD
1:0	CIM	R/W	0x0	Comparison Interrupt Mode
				This field specifies the mode by which the interrupt comparison is made.
				Value Description
				0x0 Always
				This mode generates an interrupt every time the ADC conversion data falls within the selected operational region.
				0x1 Once
				This mode generates an interrupt the first time that the ADC conversion data enters the selected operational region.
				0x2 Hysteresis Always
				This mode generates an interrupt when the ADC conversion data falls within the selected operational region and continues to generate the interrupt until the hysteresis condition is cleared by entering the opposite operational region.
				Note that the hysteresis modes are only defined for CTC encodings of 0x0 and 0x3.
				0x3 Hysteresis Once
				This mode generates an interrupt the first time that the ADC conversion data falls within the selected operational region. No additional interrupts are generated until the hysteresis condition is cleared by entering the opposite operational region.
				Note that the hysteresis modes are only defined for \mathtt{CTC} encodings of 0x0 and 0x3.

Register 52: ADC Digital Comparator Range 0 (ADCDCCMP0), offset 0xE40 Register 53: ADC Digital Comparator Range 1 (ADCDCCMP1), offset 0xE44 Register 54: ADC Digital Comparator Range 2 (ADCDCCMP2), offset 0xE48 Register 55: ADC Digital Comparator Range 3 (ADCDCCMP3), offset 0xE4C Register 56: ADC Digital Comparator Range 4 (ADCDCCMP4), offset 0xE50 Register 57: ADC Digital Comparator Range 5 (ADCDCCMP5), offset 0xE54 Register 58: ADC Digital Comparator Range 6 (ADCDCCMP6), offset 0xE58 Register 59: ADC Digital Comparator Range 7 (ADCDCCMP7), offset 0xE5C

This register defines the comparison values that are used to determine if the ADC conversion data falls in the appropriate operating region.

Note: The value in the COMP1 field must be greater than or equal to the value in the COMP0 field or unexpected results can occur.

ADC Digital Comparator Range n (ADCDCCMPn)

ADC0 base: 0x4003.8000 ADC1 base: 0x4003.9000 Offset 0xE40 Type R/W, reset 0x0000.0000

	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16
		rese	rved	1						CON	/IP1		l .			
Type	RO	RO	RO	RO	R/W	R/W	R/W	R/W	R/W	R/W						
Reset	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0
	15	14	13	12	11	10	9	8	7	6	5	4	3	2	1	0
	reserved									CON	/IP0) 	1		
Туре	RO	RO	RO	RO	R/W	R/W	R/W	R/W	R/W	R/W						
Reset	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0

Bit/Field	Name	Type	Reset	Description
31:28	reserved	RO	0x0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
27:16	COMP1	R/W	0x000	Compare 1
				The value in this field is compared against the ADC conversion data. The result of the comparison is used to determine if the data lies within the high-band region.
				Note that the value of ${\tt COMP1}$ must be greater than or equal to the value of ${\tt COMP0}.$
15:12	reserved	RO	0x0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
11:0	COMP0	R/W	0x000	Compare 0 The value in this field is compared against the ADC conversion data.

the low-band region.

The result of the comparison is used to determine if the data lies within

Register 60: ADC Peripheral Properties (ADCPP), offset 0xFC0

The **ADCPP** register provides information regarding the properties of the ADC module.

ADC Peripheral Properties (ADCPP)

ADC0 base: 0x4003.8000 ADC1 base: 0x4003.9000 Offset 0xFC0

Type RO, reset 0x00B0.2167

	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16
			1	rese	rved I				TS		1	RSL			TY	PE
Type Reset	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 1	RO 0	RO 1	RO 1	RO 0	RO 0	RO 0	RO 0
	15	14	13	12	11	10	9	8	7	6	5	4	3	2	1	0
	,		I D	C		1	'		С	H	1	ı		Ms	SR	
Type Reset	RO 0	RO 0	RO 1	RO 0	RO 0	RO 0	RO 0	RO 1	RO 0	RO 1	RO 1	RO 0	RO 0	RO 1	RO 1	RO 1
E	Bit/Field Name		Ту	/pe	Reset	Des	cription									
	31:24		reserved RO				0	com	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.							
	23		TS	i	R	RO	0x1	Temperature Sensor								
								Valu	ue Desc	ription						
								0	The	ADC mo	dule doe	es not ha	ve a tem	perature	sensor.	
								1	The	ADC mo	dule has	a tempe	erature s	ensor.		
									field pro		ne simila	r informa	tion as tl	ne legac	y DC1 re	gister
	22:18		RSI	L	R	RO	0xC	Resolution								
								This field specifies the maximum number of binary bits used to the converted sample. The field is encoded as a binary value range of 0 to 32 bits.								
	17:16		TYP	E	R	RO	0x0	ADC	2 Archite	cture						
								Valu	ue D	escription	on					
								0x0	S	AR						
								0x1	- 0x3 R	eserved	I					
	15:10		DC	;	R	RO	0x8	Digit	tal Comp	arator (Count					
									converte			er of AD(coded as				

ADCnDCn bits.

This field provides similar information to the legacy $\ensuremath{\text{DC9}}$ register

Bit/Field	Name	Туре	Reset	Description	n
9:4	СН	RO	0x16	converter. 63.	nnel Count specifies the number of ADC input channels available to the This field is encoded as a binary value, in the range of 0 to rovides similar information to the legacy DC3 and DC8 register
				ADCnAINn	
3:0	MSR	RO	0x7	Maximum	ADC Sample Rate
					specifies the maximum number of ADC conversions per ne MSR field is encoded as follows:
				Value	Description
				0x0	Reserved
				0x1	125 ksps
				0x2	Reserved
				0x3	250 ksps
				0x4	Reserved
				0x5	500 ksps
				0x6	Reserved
				0x7	1 Msps
				0x8 - 0xF	Reserved


Register 61: ADC Peripheral Configuration (ADCPC), offset 0xFC4

The ADCPC register provides information regarding the configuration of the peripheral.

ADC Peripheral Configuration (ADCPC)

ADC0 base: 0x4003.8000 ADC1 base: 0x4003.9000 Offset 0xFC4

Type R/W, reset 0x0000.0007



Bit/Field	Name	Type	Reset	Description
31:4	reserved	RO	0x0000.0000	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
3:0	SR	R/W	0x7	ADC Sample Rate

This field specifies the number of ADC conversions per second and is used in Run, Sleep, and Deep-sleep modes. The field encoding is based on the legacy **RCGC0** register encoding. The programmed sample rate cannot exceed the maximum sample rate specified by the MSR field in the **ADCPP** register. The SR field is encoded as follows:

Value	Description
0x0	Reserved
0x1	125 ksps
0x2	Reserved
0x3	250 ksps
0x4	Reserved
0x5	500 ksps
0x6	Reserved
0x7	1 Msps
0x8 - 0xF	Reserved

Register 62: ADC Clock Configuration (ADCCC), offset 0xFC8


The **ADCCC** register controls the clock source for the ADC module.

To use the PIOSC to clock the ADC, first power up the PLL and then enable the PIOSC in the CS bit field, then disable the PLL.

To use the MOSC to clock the ADC, first power up the PLL and then enable the clock to the ADC module, then disable the PLL and switch to the MOSC for the system clock.

ADC Clock Configuration (ADCCC)

ADC0 base: 0x4003.8000 ADC1 base: 0x4003.9000 Offset 0xFC8 Type R/W, reset 0x0000.0000



Bit/Field	Name	Type	Reset	Description
31:4	reserved	RO	0x0000.000	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
3:0	CS	R/W	0	ADC Clock Source
				The following table energifies the clock source that generates the ADC

The following table specifies the clock source that generates the ADC clock input, see Figure 5-5 on page 226.

Value	Description
0x0	Either the 16-MHz system clock (if the PLL bypass is in effect) or the 16 MHz clock derived from PLL ÷ 25 (default).
	Note that when the PLL is bypassed, the system clock must be at least 16 MHz.
0x1	PIOSC

The PIOSC provides a 16-MHz clock source for the ADC. If the PIOSC is used as the clock source, the ADC module can continue to operate in Deep-Sleep mode.

0x2 - 0xF Reserved

14 Universal Asynchronous Receivers/Transmitters (UARTs)


The Stellaris[®] LM4F232H5QC controller includes eight Universal Asynchronous Receiver/Transmitter (UART) with the following features:

- Programmable baud-rate generator allowing speeds up to 5 Mbps for regular speed (divide by 16) and 10 Mbps for high speed (divide by 8)
- Separate 16x8 transmit (TX) and receive (RX) FIFOs to reduce CPU interrupt service loading
- Programmable FIFO length, including 1-byte deep operation providing conventional double-buffered interface
- FIFO trigger levels of 1/8, 1/4, 1/2, 3/4, and 7/8
- Standard asynchronous communication bits for start, stop, and parity
- Line-break generation and detection
- Fully programmable serial interface characteristics
 - 5, 6, 7, or 8 data bits
 - Even, odd, stick, or no-parity bit generation/detection
 - 1 or 2 stop bit generation
- IrDA serial-IR (SIR) encoder/decoder providing
 - Programmable use of IrDA Serial Infrared (SIR) or UART input/output
 - Support of IrDA SIR encoder/decoder functions for data rates up to 115.2 Kbps half-duplex
 - Support of normal 3/16 and low-power (1.41-2.23 μs) bit durations
 - Programmable internal clock generator enabling division of reference clock by 1 to 256 for low-power mode bit duration
- Support for communication with ISO 7816 smart cards
- Modem flow control and status (on UART1)
- EIA-485 9-bit support
- Standard FIFO-level and End-of-Transmission interrupts
- Efficient transfers using Micro Direct Memory Access Controller (µDMA)
 - Separate channels for transmit and receive
 - Receive single request asserted when data is in the FIFO; burst request asserted at programmed FIFO level

 Transmit single request asserted when there is space in the FIFO; burst request asserted at programmed FIFO level

14.1 Block Diagram

Figure 14-1. UART Module Block Diagram



14.2 Signal Description

The following table lists the external signals of the UART module and describes the function of each. The UART signals are alternate functions for some GPIO signals and default to be GPIO signals at reset, with the exception of the UORX and UOTX pins which default to the UART function. The column in the table below titled "Pin Mux/Pin Assignment" lists the possible GPIO pin placements for these UART signals. The AFSEL bit in the **GPIO Alternate Function Select (GPIOAFSEL)** register (page 670) should be set to choose the UART function. The number in parentheses is the encoding that must be programmed into the PMCn field in the **GPIO Port Control (GPIOPCTL)** register (page 688) to assign the UART signal to the specified GPIO port pin. For more information on configuring GPIOs, see "General-Purpose Input/Outputs (GPIOS)" on page 646.

Table 14-1. UART Signals (100LQFP)

Pin Name	Pin Number	Pin Mux / Pin Assignment	Pin Type	Buffer Type ^a	Description
U0Rx	26	PA0 (1)	I	TTL	UART module 0 receive.

Table 14-1. UART Signals (100LQFP) (continued)

Pin Name	Pin Number	Pin Mux / Pin Assignment	Pin Type	Buffer Type ^a	Description
UOTx	27	PA1 (1)	0	TTL	UART module 0 transmit.
Ulcts	24 41	PC5 (8) PF1 (1)	1	TTL	UART module 1 Clear To Send modem flow control input signal.
U1DCD	42	PF2 (1)	I	TTL	UART module 1 Data Carrier Detect modem status input signal.
U1DSR	43	PF3 (1)	I	TTL	UART module 1 Data Set Ready modem output control line.
U1DTR	39	PF4 (1)	0	TTL	UART module 1 Data Terminal Ready modem status input signal.
UlRI	90	PE7 (1)	I	TTL	UART module 1 Ring Indicator modem status input signal.
Ulrts	25 40	PC4 (8) PF0 (1)	0	TTL	UART module 1 Request to Send modem flow control output line.
U1Rx	25 70	PC4 (2) PB0 (1)	1	TTL	UART module 1 receive.
UlTx	24 71	PC5 (2) PB1 (1)	0	TTL	UART module 1 transmit.
U2Rx	74 99	PG4 (1) PD6 (1)	I	TTL	UART module 2 receive.
U2Tx	75 100	PG5 (1) PD7 (1)	0	TTL	UART module 2 transmit.
U3Rx	23	PC6 (1)	I	TTL	UART module 3 receive.
U3Tx	22	PC7 (1)	0	TTL	UART module 3 transmit.
U4Rx	25 68	PC4 (1) PJ0 (1)	I	TTL	UART module 4 receive.
U4Tx	24 69	PC5 (1) PJ1 (1)	0	TTL	UART module 4 transmit.
U5Rx	11 95	PJ2 (1) PE4 (1)	1	TTL	UART module 5 receive.
U5Tx	96	PE5 (1)	0	TTL	UART module 5 transmit.
U6Rx	97	PD4 (1)	I	TTL	UART module 6 receive.
U6Tx	98	PD5 (1)	0	TTL	UART module 6 transmit.
U7Rx	15	PE0 (1)	I	TTL	UART module 7 receive.
U7Tx	14	PE1 (1)	0	TTL	UART module 7 transmit.

a. The TTL designation indicates the pin has TTL-compatible voltage levels.

14.3 Functional Description

Each Stellaris UART performs the functions of parallel-to-serial and serial-to-parallel conversions. It is similar in functionality to a 16C550 UART, but is not register compatible.

The UART is configured for transmit and/or receive via the TXE and RXE bits of the **UART Control** (**UARTCTL**) register (see page 924). Transmit and receive are both enabled out of reset. Before any control registers are programmed, the UART must be disabled by clearing the UARTEN bit in **UARTCTL**. If the UART is disabled during a TX or RX operation, the current transaction is completed prior to the UART stopping.


The UART module also includes a serial IR (SIR) encoder/decoder block that can be connected to an infrared transceiver to implement an IrDA SIR physical layer. The SIR function is programmed using the **UARTCTL** register.

14.3.1 Transmit/Receive Logic

The transmit logic performs parallel-to-serial conversion on the data read from the transmit FIFO. The control logic outputs the serial bit stream beginning with a start bit and followed by the data bits (LSB first), parity bit, and the stop bits according to the programmed configuration in the control registers. See Figure 14-2 on page 901 for details.

The receive logic performs serial-to-parallel conversion on the received bit stream after a valid start pulse has been detected. Overrun, parity, frame error checking, and line-break detection are also performed, and their status accompanies the data that is written to the receive FIFO.

Figure 14-2. UART Character Frame



14.3.2 Baud-Rate Generation

The baud-rate divisor is a 22-bit number consisting of a 16-bit integer and a 6-bit fractional part. The number formed by these two values is used by the baud-rate generator to determine the bit period. Having a fractional baud-rate divisor allows the UART to generate all the standard baud rates.

The 16-bit integer is loaded through the **UART Integer Baud-Rate Divisor (UARTIBRD)** register (see page 920) and the 6-bit fractional part is loaded with the **UART Fractional Baud-Rate Divisor (UARTFBRD)** register (see page 921). The baud-rate divisor (BRD) has the following relationship to the system clock (where *BRDI* is the integer part of the *BRD* and *BRDF* is the fractional part, separated by a decimal place.)

```
BRD = BRDI + BRDF = UARTSysClk / (ClkDiv * Baud Rate)
```

where <code>UARTSysClk</code> is the system clock connected to the UART, and <code>ClkDiv</code> is either 16 (if <code>HSE</code> in <code>UARTCTL</code> is clear) or 8 (if <code>HSE</code> is set). By default, this will be the main system clock described in "Clock Control" on page 223. Alternatively, the UART may be clocked from the internal precision oscillator (PIOSC), independent of the system clock selection. This will allow the UART clock to be programmed indpendently of the system clock PLL settings. See the <code>UARTCC</code> register for more details.

The 6-bit fractional number (that is to be loaded into the DIVFRAC bit field in the **UARTFBRD** register) can be calculated by taking the fractional part of the baud-rate divisor, multiplying it by 64, and adding 0.5 to account for rounding errors:

```
UARTFBRD[DIVFRAC] = integer(BRDF * 64 + 0.5)
```

The UART generates an internal baud-rate reference clock at 8x or 16x the baud-rate (referred to as Baud8 and Baud16, depending on the setting of the HSE bit (bit 5) in **UARTCTL**). This reference clock is divided by 8 or 16 to generate the transmit clock, and is used for error detection during receive operations. Note that the state of the HSE bit has no effect on clock generation in ISO 7816 smart card mode (when the SMART bit in the **UARTCTL** register is set).

Along with the **UART Line Control**, **High Byte (UARTLCRH)** register (see page 922), the **UARTIBRD** and **UARTFBRD** registers form an internal 30-bit register. This internal register is only updated when a write operation to **UARTLCRH** is performed, so any changes to the baud-rate divisor must be followed by a write to the **UARTLCRH** register for the changes to take effect.

To update the baud-rate registers, there are four possible sequences:

- UARTIBRD write, UARTFBRD write, and UARTLCRH write
- UARTFBRD write, UARTIBRD write, and UARTLCRH write
- UARTIBRD write and UARTLCRH write
- UARTFBRD write and UARTLCRH write

14.3.3 Data Transmission

Data received or transmitted is stored in two 16-byte FIFOs, though the receive FIFO has an extra four bits per character for status information. For transmission, data is written into the transmit FIFO. If the UART is enabled, it causes a data frame to start transmitting with the parameters indicated in the **UARTLCRH** register. Data continues to be transmitted until there is no data left in the transmit FIFO. The BUSY bit in the **UART Flag (UARTFR)** register (see page 916) is asserted as soon as data is written to the transmit FIFO (that is, if the FIFO is non-empty) and remains asserted while data is being transmitted. The BUSY bit is negated only when the transmit FIFO is empty, and the last character has been transmitted from the shift register, including the stop bits. The UART can indicate that it is busy even though the UART may no longer be enabled.

When the receiver is idle (the UnRx signal is continuously 1), and the data input goes Low (a start bit has been received), the receive counter begins running and data is sampled on the eighth cycle of Baud16 or fourth cycle of Baud8 depending on the setting of the HSE bit (bit 5) in **UARTCTL** (described in "Transmit/Receive Logic" on page 901).

The start bit is valid and recognized if the \mathtt{UnRx} signal is still low on the eighth cycle of $\mathtt{Baud16}$ (HSE clear) or the fourth cycle of Baud 8 (HSE set), otherwise it is ignored. After a valid start bit is detected, successive data bits are sampled on every 16th cycle of $\mathtt{Baud16}$ or 8th cycle of $\mathtt{Baud8}$ (that is, one bit period later) according to the programmed length of the data characters and value of the \mathtt{HSE} bit in **UARTCTL**. The parity bit is then checked if parity mode is enabled. Data length and parity are defined in the **UARTLCRH** register.

Lastly, a valid stop bit is confirmed if the \mathtt{UnRx} signal is High, otherwise a framing error has occurred. When a full word is received, the data is stored in the receive FIFO along with any error bits associated with that word.

14.3.4 Serial IR (SIR)

The UART peripheral includes an IrDA serial-IR (SIR) encoder/decoder block. The IrDA SIR block provides functionality that converts between an asynchronous UART data stream and a half-duplex serial SIR interface. No analog processing is performed on-chip. The role of the SIR block is to provide a digital encoded output and decoded input to the UART. When enabled, the SIR block uses the UnTx and UnRx pins for the SIR protocol. These signals should be connected to an infrared transceiver to implement an IrDA SIR physical layer link. The SIR block can receive and transmit, but it is only half-duplex so it cannot do both at the same time. Transmission must be stopped before data can be received. The IrDA SIR physical layer specifies a minimum 10-ms delay between transmission and reception. The SIR block has two modes of operation:

- In normal IrDA mode, a zero logic level is transmitted as a high pulse of 3/16th duration of the selected baud rate bit period on the output pin, while logic one levels are transmitted as a static LOW signal. These levels control the driver of an infrared transmitter, sending a pulse of light for each zero. On the reception side, the incoming light pulses energize the photo transistor base of the receiver, pulling its output LOW and driving the UART input pin LOW.
- In low-power IrDA mode, the width of the transmitted infrared pulse is set to three times the period of the internally generated IrLPBaud16 signal (1.63 μs, assuming a nominal 1.8432 MHz frequency) by changing the appropriate bit in the **UARTCR** register. See page 919 for more information on IrDA low-power pulse-duration configuration.

Whether the device is in normal or low-power IrDA mode, a start bit is deemed valid if the decoder is still Low, one period of IrLPBaud16 after the Low was first detected. This enables a normal-mode UART to receive data from a low-power mode UART that can transmit pulses as small as 1.41 μ s. Thus, for both low-power and normal mode operation, the ILPDVSR field in the **UARTILPR** register must be programmed such that 1.42 MHz < F_IrLPBaud16 < 2.12 MHz, resulting in a low-power pulse duration of 1.41–2.11 μ s (three times the period of IrLPBaud16). The minimum frequency of IrLPBaud16 ensures that pulses less than one period of IrLPBaud16 are rejected, but pulses greater than 1.4 μ s are accepted as valid pulses.

Figure 14-3 on page 903 shows the UART transmit and receive signals, with and without IrDA modulation.




Figure 14-3. IrDA Data Modulation

In both normal and low-power IrDA modes:

- During transmission, the UART data bit is used as the base for encoding
- During reception, the decoded bits are transferred to the UART receive logic

The IrDA SIR physical layer specifies a half-duplex communication link, with a minimum 10-ms delay between transmission and reception. This delay must be generated by software because it is not automatically supported by the UART. The delay is required because the infrared receiver electronics might become biased or even saturated from the optical power coupled from the adjacent transmitter LED. This delay is known as latency or receiver setup time.

14.3.5 ISO 7816 Support

The UART offers basic support to allow communication with an ISO 7816 smartcard. When bit 3 (SMART) of the **UARTCTL** register is set, the UnTx signal is used as a bit clock, and the UnRx signal is used as the half-duplex communication line connected to the smartcard. A GPIO signal can be used to generate the reset signal to the smartcard. The remaining smartcard signals should be provided by the system design. The maximum clock rate in this mode is system clock / 16.

When using ISO 7816 mode, the **UARTLCRH** register must be set to transmit 8-bit words (WLEN bits 6:5 configured to 0x3) with EVEN parity (PEN set and EPS set). In this mode, the UART automatically uses 2 stop bits, and the STP2 bit of the **UARTLCRH** register is ignored.

If a parity error is detected during transmission, UnRx is pulled Low during the second stop bit. In this case, the UART aborts the transmission, flushes the transmit FIFO and discards any data it contains, and raises a parity error interrupt, allowing software to detect the problem and initiate retransmission of the affected data. Note that the UART does not support automatic retransmission in this case.

14.3.6 Modem Handshake Support

This section describes how to configure and use the modem flow control and status signals for UART1 when connected as a DTE (data terminal equipment) or as a DCE (data communications equipment). In general, a modem is a DCE and a computing device that connects to a modem is the DTE.

14.3.6.1 **Signaling**

The status signals provided by UART1 differ based on whether the UART is used as a DTE or DCE. When used as a DTE, the modem flow control and status signals are defined as:

- ŪICTS is Clear To Send
- U1DSR is Data Set Ready
- Ū1DCD is Data Carrier Detect
- UIRI is Ring Indicator
- ŪIRTS is Request To Send
- Ū1DTR is Data Terminal Ready

When used as a DCE, the the modem flow control and status signals are defined as:

- ŪICTS is Request To Send
- UIDSR is Data Terminal Ready
- UIRTS is Clear To Send
- ŪIDTR is Data Set Ready

Note that the support for DCE functions Data Carrier Detect and Ring Indicator are not provided. If these signals are required, their function can be emulated by using a general-purpose I/O signal and providing software support.

14.3.6.2 Flow Control

Flow control can be accomplished by either hardware or software. The following sections describe the different methods.

Hardware Flow Control (RTS/CTS)

Hardware flow control between two devices is accomplished by connecting the $\overline{\mathtt{UIRTS}}$ output to the Clear-To-Send input on the receiving device, and connecting the Request-To-Send output on the receiving device to the $\overline{\mathtt{UICTS}}$ input.

The $\overline{\mathtt{U1CTS}}$ input controls the transmitter. The transmitter may only transmit data when the $\overline{\mathtt{U1CTS}}$ input is asserted. The $\overline{\mathtt{U1RTS}}$ output signal indicates the state of the receive FIFO. $\overline{\mathtt{U1CTS}}$ remains asserted until the preprogrammed watermark level is reached, indicating that the Receive FIFO has no space to store additional characters.

The **UARTCTL** register bits 15 (CTSEN) and 14 (RTSEN) specify the flow control mode as shown in Table 14-2 on page 905.

Table 14-2. Flow Control M	ode
----------------------------	-----

CTSEN	RTSEN	Description
1	1	RTS and CTS flow control enabled
1	0	Only CTS flow control enabled
0	1	Only RTS flow control enabled
0	0	Both RTS and CTS flow control disabled

Note that when RTSEN is 1, software cannot modify the $\overline{\mathtt{UIRTS}}$ output value through the **UARTCTL** register Request to Send (RTS) bit, and the status of the RTS bit should be ignored.

Software Flow Control (Modem Status Interrupts)

Software flow control between two devices is accomplished by using interrupts to indicate the status of the UART. Interrupts may be generated for the $\overline{\mathtt{UIDSR}}$, $\overline{\mathtt{UIDCD}}$, $\overline{\mathtt{UICTS}}$, and $\overline{\mathtt{UIRI}}$ signals using bits 3:0 of the **UARTIM** register, respectively. The raw and masked interrupt status may be checked using the **UARTRIS** and **UARTMIS** register. These interrupts may be cleared using the **UARTICR** register.

14.3.7 9-Bit UART Mode

The UART provides a 9-bit mode that is enabled with the 9BITEN bit in the **UART9BITADDR** register. This feature is useful in a multi-drop configuration of the UART where a single master connected to multiple slaves can communicate with a particular slave through its address or set of addresses along with a qualifier for an address byte. All the slaves check for the address qualifier in the place of the parity bit and, if set, then compare the byte received with the preprogrammed address. If the address matches, then it receives or sends further data. If the address does not match, it drops the address byte and any subsequent data bytes. If the UART is in 9-bit mode, then the receiver operates with no parity mode. The address can be predefined to match with the received byte and it can be configured with the **UART9BITADDR** register. The matching can be extended to a set of addresses using the address mask in the **UART9BITAMASK** register. By default, the **UART9BITAMASK** is 0xFF, meaning that only the specified address is matched.

When not finding a match, the rest of the data bytes with the 9th bit cleared are dropped. If a match is found, then an interrupt is generated to the NVIC for further action. The subsequent data bytes with the cleared 9th bit are stored in the FIFO. Software can mask this interrupt in case μ DMA and/or FIFO operations are enabled for this instance and processor intervention is not required. All the

send transactions with 9-bit mode are data bytes and the 9th bit is cleared. Software can override the 9th bit to be set (to indicate address) by overriding the parity settings to sticky parity with odd parity enabled for a particular byte. To match the transmission time with correct parity settings, the address byte can be transmitted as a single then a burst transfer. The Transmit FIFO does not hold the address/data bit, hence software should take care of enabling the address bit appropriately.

14.3.8 FIFO Operation

The UART has two 16x8 FIFOs; one for transmit and one for receive. Both FIFOs are accessed via the **UART Data (UARTDR)** register (see page 911). Read operations of the **UARTDR** register return a 12-bit value consisting of 8 data bits and 4 error flags while write operations place 8-bit data in the transmit FIFO.

Out of reset, both FIFOs are disabled and act as 1-byte-deep holding registers. The FIFOs are enabled by setting the FEN bit in **UARTLCRH** (page 922).

FIFO status can be monitored via the **UART Flag (UARTFR)** register (see page 916) and the **UART Receive Status (UARTRSR)** register. Hardware monitors empty, full and overrun conditions. The **UARTFR** register contains empty and full flags (TXFE, TXFF, RXFE, and RXFF bits), and the **UARTRSR** register shows overrun status via the OE bit. If the FIFOs are disabled, the empty and full flags are set according to the status of the 1-byte-deep holding registers.

The trigger points at which the FIFOs generate interrupts is controlled via the **UART Interrupt FIFO Level Select (UARTIFLS)** register (see page 928). Both FIFOs can be individually configured to trigger interrupts at different levels. Available configurations include ½, ¼, ½, ¾, and ⅙. For example, if the ¼ option is selected for the receive FIFO, the UART generates a receive interrupt after 4 data bytes are received. Out of reset, both FIFOs are configured to trigger an interrupt at the ½ mark.

14.3.9 Interrupts

The UART can generate interrupts when the following conditions are observed:

- Overrun Error
- Break Error
- Parity Error
- Framing Error
- Receive Timeout
- Transmit (when condition defined in the TXIFLSEL bit in the **UARTIFLS** register is met, or if the EOT bit in **UARTCTL** is set, when the last bit of all transmitted data leaves the serializer)
- Receive (when condition defined in the RXIFLSEL bit in the **UARTIFLS** register is met)

All of the interrupt events are ORed together before being sent to the interrupt controller, so the UART can only generate a single interrupt request to the controller at any given time. Software can service multiple interrupt events in a single interrupt service routine by reading the **UART Masked Interrupt Status (UARTMIS)** register (see page 936).

The interrupt events that can trigger a controller-level interrupt are defined in the **UART Interrupt Mask (UARTIM)** register (see page 930) by setting the corresponding IM bits. If interrupts are not used, the raw interrupt status is always visible via the **UART Raw Interrupt Status (UARTRIS)** register (see page 933).

Interrupts are always cleared (for both the **UARTMIS** and **UARTRIS** registers) by writing a 1 to the corresponding bit in the **UART Interrupt Clear (UARTICR)** register (see page 939).

The receive timeout interrupt is asserted when the receive FIFO is not empty, and no further data is received over a 32-bit period. The receive timeout interrupt is cleared either when the FIFO becomes empty through reading all the data (or by reading the holding register), or when a 1 is written to the corresponding bit in the **UARTICR** register.

The receive interrupt changes state when one of the following events occurs:

- If the FIFOs are enabled and the receive FIFO reaches the programmed trigger level, the RXRIS bit is set. The receive interrupt is cleared by reading data from the receive FIFO until it becomes less than the trigger level, or by clearing the interrupt by writing a 1 to the RXIC bit.
- If the FIFOs are disabled (have a depth of one location) and data is received thereby filling the location, the RXRIS bit is set. The receive interrupt is cleared by performing a single read of the receive FIFO, or by clearing the interrupt by writing a 1 to the RXIC bit.

The transmit interrupt changes state when one of the following events occurs:

- If the FIFOs are enabled and the transmit FIFO reaches the programmed trigger level, the TXRIS bit is set. The transmit interrupt is cleared by writing data to the transmit FIFO until it becomes greater than the trigger level, or by clearing the interrupt by writing a 1 to the TXIC bit.
- If the FIFOs are disabled (have a depth of one location) and there is no data present in the transmitters single location, the TXRIS bit is set. It is cleared by performing a single write to the transmit FIFO, or by clearing the interrupt by writing a 1 to the TXIC bit.

14.3.10 Loopback Operation

The UART can be placed into an internal loopback mode for diagnostic or debug work by setting the LBE bit in the **UARTCTL** register (see page 924). In loopback mode, data transmitted on the \mathtt{UnTx} output is received on the \mathtt{UnRx} input. Note that the LBE bit should be set before the UART is enabled.

14.3.11 DMA Operation

The UART provides an interface to the μ DMA controller with separate channels for transmit and receive. The DMA operation of the UART is enabled through the **UART DMA Control** (**UARTDMACTL**) register. When DMA operation is enabled, the UART asserts a DMA request on the receive or transmit channel when the associated FIFO can transfer data. For the receive channel, a single transfer request is asserted whenever any data is in the receive FIFO. A burst transfer request is asserted whenever the amount of data in the receive FIFO is at or above the FIFO trigger level configured in the **UARTIFLS** register. For the transmit channel, a single transfer request is asserted whenever there is at least one empty location in the transmit FIFO. The burst request is asserted whenever the transmit FIFO contains fewer characters than the FIFO trigger level. The single and burst DMA transfer requests are handled automatically by the μ DMA controller depending on how the DMA channel is configured.

To enable DMA operation for the receive channel, set the RXDMAE bit of the **DMA Control** (**UARTDMACTL**) register. To enable DMA operation for the transmit channel, set the TXDMAE bit of the **UARTDMACTL** register. The UART can also be configured to stop using DMA for the receive channel if a receive error occurs. If the DMAERR bit of the **UARTDMACR** register is set and a receive error occurs, the DMA receive requests are automatically disabled. This error condition can be cleared by clearing the appropriate UART error interrupt.

If DMA is enabled, then the μ DMA controller triggers an interrupt when a transfer is complete. The interrupt occurs on the UART interrupt vector. Therefore, if interrupts are used for UART operation and DMA is enabled, the UART interrupt handler must be designed to handle the μ DMA completion interrupt.

See "Micro Direct Memory Access (μ DMA)" on page 582 for more details about programming the μ DMA controller.

14.4 Initialization and Configuration

To enable and initialize the UART, the following steps are necessary:

- 1. Enable the UART module using the **RCGCUART** register (see page 335).
- **2.** Enable the clock to the appropriate GPIO module via the **RCGCGPIO** register (see page 330). To find out which GPIO port to enable, refer to Table 23-5 on page 1367.
- 3. Set the GPIO AFSEL bits for the appropriate pins (see page 670). To determine which GPIOs to configure, see Table 23-4 on page 1358.
- **4.** Configure the GPIO current level and/or slew rate as specified for the mode selected (see page 672 and page 680).
- **5.** Configure the PMCn fields in the **GPIOPCTL** register to assign the UART signals to the appropriate pins (see page 688 and Table 23-5 on page 1367).

To use the UART, the peripheral clock must be enabled by setting the appropriate bit in the **RCGCUART** register (page 335). In addition, the clock to the appropriate GPIO module must be enabled via the **RCGCGPIO** register (page 330) in the System Control module. To find out which GPIO port to enable, refer to Table 23-5 on page 1367.

This section discusses the steps that are required to use a UART module. For this example, the UART clock is assumed to be 20 MHz, and the desired UART configuration is:

- 115200 baud rate
- Data length of 8 bits
- One stop bit
- No parity
- FIFOs disabled
- No interrupts

The first thing to consider when programming the UART is the baud-rate divisor (BRD), because the **UARTIBRD** and **UARTFBRD** registers must be written before the **UARTLCRH** register. Using the equation described in "Baud-Rate Generation" on page 901, the BRD can be calculated:

```
BRD = 20,000,000 / (16 * 115,200) = 10.8507
```

which means that the DIVINT field of the **UARTIBRD** register (see page 920) should be set to 10 decimal or 0xA. The value to be loaded into the **UARTFBRD** register (see page 921) is calculated by the equation:

```
UARTFBRD[DIVFRAC] = integer(0.8507 * 64 + 0.5) = 54
```

With the BRD values in hand, the UART configuration is written to the module in the following order:

- 1. Disable the UART by clearing the UARTEN bit in the **UARTCTL** register.
- 2. Write the integer portion of the BRD to the **UARTIBRD** register.
- 3. Write the fractional portion of the BRD to the **UARTFBRD** register.
- **4.** Write the desired serial parameters to the **UARTLCRH** register (in this case, a value of 0x0000.0060).
- 5. Configure the UART clock source by writing to the **UARTCC** register.
- **6.** Optionally, configure the μDMA channel (see "Micro Direct Memory Access (μDMA)" on page 582) and enable the DMA option(s) in the **UARTDMACTL** register.
- 7. Enable the UART by setting the UARTEN bit in the **UARTCTL** register.

14.5 Register Map

Table 14-3 on page 909 lists the UART registers. The offset listed is a hexadecimal increment to the register's address, relative to that UART's base address:

■ UART0: 0x4000.C000

■ UART1: 0x4000.D000

■ UART2: 0x4000.E000

■ UART3: 0x4000.F000

■ UART4: 0x4001.0000

■ UART5: 0x4001.1000

■ UART6: 0x4001.2000

■ UART7: 0x4001.3000

The UART module clock must be enabled before the registers can be programmed (see page 335). There must be a delay of 3 system clocks after the UART module clock is enabled before any UART module registers are accessed.

The UART must be disabled (see the UARTEN bit in the **UARTCTL** register on page 924) before any of the control registers are reprogrammed. When the UART is disabled during a TX or RX operation, the current transaction is completed prior to the UART stopping.

Table 14-3. UART Register Map

Offset	Name	Туре	Reset	Description	See page
0x000	UARTDR	R/W	0x0000.0000	UART Data	911
0x004	UARTRSR/UARTECR	R/W	0x0000.0000	UART Receive Status/Error Clear	913
0x018	UARTFR	RO	0x0000.0090	UART Flag	916
0x020	UARTILPR	R/W	0x0000.0000	UART IrDA Low-Power Register	919
0x024	UARTIBRD	R/W	0x0000.0000	UART Integer Baud-Rate Divisor	920
0x028	UARTFBRD	R/W	0x0000.0000	UART Fractional Baud-Rate Divisor	921
0x02C	UARTLCRH	R/W	0x0000.0000	UART Line Control	922

Table 14-3. UART Register Map (continued)

Offset	Name	Туре	Reset	Description	See page
0x030	UARTCTL	R/W	0x0000.0300	UART Control	924
0x034	UARTIFLS	R/W	0x0000.0012	UART Interrupt FIFO Level Select	928
0x038	UARTIM	R/W	0x0000.0000	UART Interrupt Mask	930
0x03C	UARTRIS	RO	0x0000.0000	UART Raw Interrupt Status	933
0x040	UARTMIS	RO	0x0000.0000	UART Masked Interrupt Status	936
0x044	UARTICR	W1C	0x0000.0000	UART Interrupt Clear	939
0x048	UARTDMACTL	R/W	0x0000.0000	UART DMA Control	941
0x0A4	UART9BITADDR	R/W	0x0000.0000	UART 9-Bit Self Address	942
0x0A8	UART9BITAMASK	R/W	0x0000.00FF	UART 9-Bit Self Address Mask	943
0xFC0	UARTPP	RO	0x0000.0003	UART Peripheral Properties	944
0xFC8	UARTCC	R/W	0x0000.0000	UART Clock Configuration	945
0xFD0	UARTPeriphID4	RO	0x0000.0000	UART Peripheral Identification 4	946
0xFD4	UARTPeriphID5	RO	0x0000.0000	UART Peripheral Identification 5	947
0xFD8	UARTPeriphID6	RO	0x0000.0000	UART Peripheral Identification 6	948
0xFDC	UARTPeriphID7	RO	0x0000.0000	UART Peripheral Identification 7	949
0xFE0	UARTPeriphID0	RO	0x0000.0060	UART Peripheral Identification 0	950
0xFE4	UARTPeriphID1	RO	0x0000.0000	UART Peripheral Identification 1	951
0xFE8	UARTPeriphID2	RO	0x0000.0018	UART Peripheral Identification 2	952
0xFEC	UARTPeriphID3	RO	0x0000.0001	UART Peripheral Identification 3	953
0xFF0	UARTPCellID0	RO	0x0000.000D	UART PrimeCell Identification 0	954
0xFF4	UARTPCellID1	RO	0x0000.00F0	UART PrimeCell Identification 1	955
0xFF8	UARTPCellID2	RO	0x0000.0005	UART PrimeCell Identification 2	956
0xFFC	UARTPCellID3	RO	0x0000.00B1	UART PrimeCell Identification 3	957

14.6 Register Descriptions

The remainder of this section lists and describes the UART registers, in numerical order by address offset.

Register 1: UART Data (UARTDR), offset 0x000

Important: This register is read-sensitive. See the register description for details.

This register is the data register (the interface to the FIFOs).


For transmitted data, if the FIFO is enabled, data written to this location is pushed onto the transmit FIFO. If the FIFO is disabled, data is stored in the transmitter holding register (the bottom word of the transmit FIFO). A write to this register initiates a transmission from the UART.

For received data, if the FIFO is enabled, the data byte and the 4-bit status (break, frame, parity, and overrun) is pushed onto the 12-bit wide receive FIFO. If the FIFO is disabled, the data byte and status are stored in the receiving holding register (the bottom word of the receive FIFO). The received data can be retrieved by reading this register.

UART Data (UARTDR)

UART0 base: 0x4000.C000 UART1 base: 0x4000.D000 UART2 base: 0x4000.E000 UART3 base: 0x4000.F000 UART4 base: 0x4001.0000 UART5 base: 0x4001.1000 UART6 base: 0x4001.2000 UART7 base: 0x4001.3000 Offset 0x000

Type R/W, reset 0x0000.0000



Bit/Field	Name	Type	Reset	Description
31:12	reserved	RO	0x0000.0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
11	OE	RO	0	UART Overrun Error

Value Description

- 0 No data has been lost due to a FIFO overrun.
- New data was received when the FIFO was full, resulting in data loss.

Bit/Field	Name	Туре	Reset	Description
10	BE	RO	0	UART Break Error
				Value Description O No break condition has occurred
				A break condition has been detected, indicating that the receive data input was held Low for longer than a full-word transmission time (defined as start, data, parity, and stop bits).
				In FIFO mode, this error is associated with the character at the top of the FIFO. When a break occurs, only one 0 character is loaded into the FIFO. The next character is only enabled after the received data input goes to a 1 (marking state), and the next valid start bit is received.
9	PE	RO	0	UART Parity Error
				Value Description
				0 No parity error has occurred
				The parity of the received data character does not match the parity defined by bits 2 and 7 of the UARTLCRH register.
				In FIFO mode, this error is associated with the character at the top of the FIFO.
8	FE	RO	0	UART Framing Error
				Value Description
				0 No framing error has occurred
				1 The received character does not have a valid stop bit (a valid stop bit is 1).
7:0	DATA	R/W	0x00	Data Transmitted or Received Data that is to be transmitted via the UART is written to this field. When read, this field contains the data that was received by the UART.

Register 2: UART Receive Status/Error Clear (UARTRSR/UARTECR), offset 0x004

The **UARTRSR/UARTECR** register is the receive status register/error clear register.

In addition to the **UARTDR** register, receive status can also be read from the **UARTRSR** register. If the status is read from this register, then the status information corresponds to the entry read from **UARTDR** prior to reading **UARTRSR**. The status information for overrun is set immediately when an overrun condition occurs.

The **UARTRSR** register cannot be written.


A write of any value to the **UARTECR** register clears the framing, parity, break, and overrun errors. All the bits are cleared on reset.

Read-Only Status Register

UART Receive Status/Error Clear (UARTRSR/UARTECR)

UART0 base: 0x4000.C000 UART1 base: 0x4000.D000 UART2 base: 0x4000.E000 UART3 base: 0x4000.F000 UART4 base: 0x4001.0000 UART5 base: 0x4001.1000 UART6 base: 0x4001.2000 UART7 base: 0x4001.3000 Offset 0x004

Type RO, reset 0x0000.0000



Bit/Field	Name	Type	Reset	Description
31:4	reserved	RO	0x0000.000	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
3	OE	RO	0	UART Overrun Error

Value Description

- 0 No data has been lost due to a FIFO overrun.
- New data was received when the FIFO was full, resulting in data loss.

This bit is cleared by a write to **UARTECR**.

The FIFO contents remain valid because no further data is written when the FIFO is full, only the contents of the shift register are overwritten. The CPU must read the data in order to empty the FIFO.

Bit/Field	Name	Туре	Reset	Description
2	BE	RO	0	UART Break Error
				Value Description
				0 No break condition has occurred
				A break condition has been detected, indicating that the receive data input was held Low for longer than a full-word transmission time (defined as start, data, parity, and stop bits).
				This bit is cleared to 0 by a write to UARTECR .
				In FIFO mode, this error is associated with the character at the top of the FIFO. When a break occurs, only one 0 character is loaded into the FIFO. The next character is only enabled after the receive data input goes to a 1 (marking state) and the next valid start bit is received.
1	PE	RO	0	UART Parity Error
				Value Description
				0 No parity error has occurred
				The parity of the received data character does not match the parity defined by bits 2 and 7 of the UARTLCRH register.
				This bit is cleared to 0 by a write to UARTECR .
0	FE	RO	0	UART Framing Error
				Value Description

- 0 No framing error has occurred
- The received character does not have a valid stop bit (a valid stop bit is 1).

This bit is cleared to 0 by a write to $\boldsymbol{\mathsf{UARTECR}}.$


In FIFO mode, this error is associated with the character at the top of the FIFO.

Write-Only Error Clear Register

UART Receive Status/Error Clear (UARTRSR/UARTECR)

UART0 base: 0x4000.C000 UART1 base: 0x4000.D000 UART2 base: 0x4000.E000 UART3 base: 0x4000.F000 UART4 base: 0x4001.0000 UART5 base: 0x4001.1000 UART6 base: 0x4001.2000 UART7 base: 0x4001.3000 Offset 0x004

Type WO, reset 0x0000.0000



Bit/Field	Name	Туре	Reset	Description
31:8	reserved	WO	0x0000.00	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
7:0	DATA	WO	0x00	Error Clear A write to this register of any data clears the framing, parity, break, and overrun flags.

Register 3: UART Flag (UARTFR), offset 0x018

The **UARTFR** register is the flag register. After reset, the TXFF, RXFF, and BUSY bits are 0, and TXFE and RXFE bits are 1. The RI, DCD, DSR and CTS bits indicate the modem flow control and status. Note that the modem bits are only implemented on UART1 and are reserved on UART0 and UART2.


UART Flag (UARTFR)

UART0 base: 0x4000.C000 UART1 base: 0x4000.D000 UART2 base: 0x4000.E000 UART3 base: 0x4000.F000 UART4 base: 0x4001.0000 UART5 base: 0x4001.1000 UART6 base: 0x4001.2000 UART7 base: 0x4001.3000 Offset 0x018

0

0

Reset



0

Bit/Field	Name	Туре	Reset	Description
31:9	reserved	RO	0x0000.00	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
8	RI	RO	0	Ring Indicator
				Value Description O The ulri signal is not asserted.
				The UIRI signal is asserted. The uiri signal is asserted.
				This bit is implemented only on UART1 and is reserved for UART0 and UART2.
7	TXFE	RO	1	UART Transmit FIFO Empty
				The meaning of this bit depends on the state of the FEN bit in the UARTLCRH register.

Value Description

- 0 The transmitter has data to transmit.
- 1 If the FIFO is disabled (FEN is 0), the transmit holding register is empty.

If the FIFO is enabled (FEN is 1), the transmit FIFO is empty.

0

0

Bit/Field	Name	Туре	Reset	Description
6	RXFF	RO	0	UART Receive FIFO Full
				The meaning of this bit depends on the state of the ${\tt FEN}$ bit in the ${\tt UARTLCRH}$ register.
				Value Description
				0 The receiver can receive data.
				1 If the FIFO is disabled (FEN is 0), the receive holding register is full.
				If the FIFO is enabled (FEN is 1), the receive FIFO is full.
5	TXFF	RO	0	UART Transmit FIFO Full
				The meaning of this bit depends on the state of the ${\tt FEN}$ bit in the ${\tt UARTLCRH}$ register.
				Value Description
				0 The transmitter is not full.
				1 If the FIFO is disabled (FEN is 0), the transmit holding register is full.
				If the FIFO is enabled (FEN is 1), the transmit FIFO is full.
4	RXFE	RO	1	UART Receive FIFO Empty
				The meaning of this bit depends on the state of the \mathtt{FEN} bit in the UARTLCRH register.
				Value Description
				0 The receiver is not empty.
				1 If the FIFO is disabled (FEN is 0), the receive holding register is empty.
				If the FIFO is enabled (FEN is 1), the receive FIFO is empty.
3	BUSY	RO	0	UART Busy
				Value Description
				0 The UART is not busy.
				The UART is busy transmitting data. This bit remains set until the complete byte, including all stop bits, has been sent from the shift register.
				This bit is set as soon as the transmit FIFO becomes non-empty (regardless of whether UART is enabled).
2	DCD	RO	0	Data Carrier Detect
				Value Description
				0 The U1DCD signal is not asserted.
				1 The U1DCD signal is asserted.
				This bit is implemented only on UART1 and is reserved for UART0 and UART2.

February 20, 2013 917

Bit/Field	Name	Туре	Reset	Description
1	DSR	RO	0	Data Set Ready
				Value Description
				0 The uldsr signal is not asserted.
				1 The U1DSR signal is asserted.
				This bit is implemented only on UART1 and is reserved for UART0 and UART2.
0	CTS	RO	0	Clear To Send
				Value Description
				0 The ulcts signal is not asserted.
				1 The U1CTS signal is asserted.
				This bit is implemented only on UART1 and is reserved for UART0 and UART2.

Register 4: UART IrDA Low-Power Register (UARTILPR), offset 0x020

The **UARTILPR** register stores the 8-bit low-power counter divisor value used to derive the low-power SIR pulse width clock by dividing down the system clock (SysClk). All the bits are cleared when reset.

The internal IrlPBaud16 clock is generated by dividing down SysClk according to the low-power divisor value written to **UARTILPR**. The duration of SIR pulses generated when low-power mode is enabled is three times the period of the IrlPBaud16 clock. The low-power divisor value is calculated as follows:

```
ILPDVSR = SysClk / F_{IrLPBaud16}
```

where $F_{IrlPBaud16}$ is nominally 1.8432 MHz.


Because the IrlPBaud16 clock is used to sample transmitted data irrespective of mode, the ILPDVSR field must be programmed in both low power and normal mode, such that 1.42 MHz < $F_{IrlPBaud16}$ < 2.12 MHz, resulting in a low-power pulse duration of 1.41–2.11 μ s (three times the period of IrlPBaud16). The minimum frequency of IrlPBaud16 ensures that pulses less than one period of IrlPBaud16 are rejected, but pulses greater than 1.4 μ s are accepted as valid pulses.

Note: Zero is an illegal value. Programming a zero value results in no IrlpBaud16 pulses being generated.

UART IrDA Low-Power Register (UARTILPR)

UART0 base: 0x4000.C000 UART1 base: 0x4000.D000 UART2 base: 0x4000.E000 UART3 base: 0x4000.F000 UART4 base: 0x4001.0000 UART5 base: 0x4001.1000 UART6 base: 0x4001.2000 UART7 base: 0x4001.3000 Offset 0x020

Type R/W, reset 0x0000.0000



Bit/Field	Name	Type	Reset	Description
31:8	reserved	RO	0x0000.00	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
7:0	ILPDVSR	R/W	0x00	IrDA Low-Power Divisor
				This field contains the 8-bit low-power divisor value.


Register 5: UART Integer Baud-Rate Divisor (UARTIBRD), offset 0x024

The **UARTIBRD** register is the integer part of the baud-rate divisor value. All the bits are cleared on reset. The minimum possible divide ratio is 1 (when **UARTIBRD**=0), in which case the **UARTFBRD** register is ignored. When changing the **UARTIBRD** register, the new value does not take effect until transmission/reception of the current character is complete. Any changes to the baud-rate divisor must be followed by a write to the **UARTLCRH** register. See "Baud-Rate Generation" on page 901 for configuration details.

UART Integer Baud-Rate Divisor (UARTIBRD)

UART0 base: 0x4000.C000 UART1 base: 0x4000.D000 UART2 base: 0x4000.E000 UART3 base: 0x4000.F000 UART4 base: 0x4001.0000 UART5 base: 0x4001.1000 UART6 base: 0x4001.2000 UART7 base: 0x4001.3000

Offset 0x024 Type R/W, reset 0x0000.0000



Bit/Field	name	туре	Reset	Description
31:16	reserved	RO	0x0000	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
15:0	DIVINT	R/W	0x0000	Integer Baud-Rate Divisor


Register 6: UART Fractional Baud-Rate Divisor (UARTFBRD), offset 0x028

The **UARTFBRD** register is the fractional part of the baud-rate divisor value. All the bits are cleared on reset. When changing the **UARTFBRD** register, the new value does not take effect until transmission/reception of the current character is complete. Any changes to the baud-rate divisor must be followed by a write to the **UARTLCRH** register. See "Baud-Rate Generation" on page 901 for configuration details.

UART Fractional Baud-Rate Divisor (UARTFBRD)

UART0 base: 0x4000.C000 UART1 base: 0x4000.D000 UART2 base: 0x4000.E000 UART3 base: 0x4000.F000 UART4 base: 0x4001.0000 UART5 base: 0x4001.1000 UART6 base: 0x4001.2000 UART7 base: 0x4001.3000 Offset 0x028

Type R/W, reset 0x0000.0000



Bit/Field	Name	Type	Reset	Description
31:6	reserved	RO	0x0000.000	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
5:0	DIVFRAC	R/W	0x0	Fractional Baud-Rate Divisor

Register 7: UART Line Control (UARTLCRH), offset 0x02C

The **UARTLCRH** register is the line control register. Serial parameters such as data length, parity, and stop bit selection are implemented in this register.

When updating the baud-rate divisor (**UARTIBRD** and/or **UARTIFRD**), the **UARTLCRH** register must also be written. The write strobe for the baud-rate divisor registers is tied to the **UARTLCRH** register.


UART Line Control (UARTLCRH)

UART0 base: 0x4000.C000 UART1 base: 0x4000.D000 UART2 base: 0x4000.E000 UART3 base: 0x4000.F000 UART4 base: 0x4001.0000

UART5 base: 0x4001.1000 UART6 base: 0x4001.2000 UART7 base: 0x4001.3000

Offset 0x02C

Type R/W, reset 0x0000.0000



Bit/Field	Name	Туре	Reset	Description	
31:8	reserved	RO	0x0000.00	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.	
7	SPS	R/W	0	UART Stick Parity Select When bits 1, 2, and 7 of UARTLCRH are set, the parity bit is transmitted and checked as a 0. When bits 1 and 7 are set and 2 is cleared, the parity bit is transmitted and checked as a 1. When this bit is cleared, stick parity is disabled.	
6:5	WLEN	R/W	0x0	UART Word Length The bits indicate the number of data bits transmitted or received in a frame as follows: Value Description	

0x0 5 bits (default)
0x1 6 bits
0x2 7 bits

8 bits

0x3

Bit/Field	Name	Туре	Reset	Description
4	FEN	R/W	0	UART Enable FIFOs
				Value Description
				The FIFOs are disabled (Character mode). The FIFOs become 1-byte-deep holding registers.
				1 The transmit and receive FIFO buffers are enabled (FIFO mode).
3	STP2	R/W	0	UART Two Stop Bits Select
				Value Description
				One stop bit is transmitted at the end of a frame.
				Two stop bits are transmitted at the end of a frame. The receive logic does not check for two stop bits being received.
				When in 7816 smartcard mode (the SMART bit is set in the UARTCTL register), the number of stop bits is forced to 2.
2	EPS	R/W	0	UART Even Parity Select
				Value Description
				Odd parity is performed, which checks for an odd number of 1s.
				Even parity generation and checking is performed during transmission and reception, which checks for an even number of 1s in data and parity bits.
				This bit has no effect when parity is disabled by the \mathtt{PEN} bit.
1	PEN	R/W	0	UART Parity Enable
				Value Description
				0 Parity is disabled and no parity bit is added to the data frame.
				1 Parity checking and generation is enabled.
0	BRK	R/W	0	UART Send Break
				Value Description
				0 Normal use.
				A Low level is continually output on the UnTx signal, after completing transmission of the current character. For the proper execution of the break command, software must set this bit for at least two frames (character periods).

February 20, 2013 923

Register 8: UART Control (UARTCTL), offset 0x030

The **UARTCTL** register is the control register. All the bits are cleared on reset except for the Transmit Enable (TXE) and Receive Enable (RXE) bits, which are set.

To enable the UART module, the UARTEN bit must be set. If software requires a configuration change in the module, the UARTEN bit must be cleared before the configuration changes are written. If the UART is disabled during a transmit or receive operation, the current transaction is completed prior to the UART stopping.

Note that bits [15:14,11:10] are only implemented on UART1. These bits are reserved on UART0 and UART2.

The **UARTCTL** register should not be changed while the UART is enabled or else the results are unpredictable. The following sequence is recommended for making changes to the **UARTCTL** register.


- Disable the UART.
- Wait for the end of transmission or reception of the current character.
- 3. Flush the transmit FIFO by clearing bit 4 (FEN) in the line control register (UARTLCRH).
- Reprogram the control register.

Enable the UART.

UART Control (UARTCTL)

UART0 base: 0x4000.C000 UART1 base: 0x4000.D000 UART2 base: 0x4000.E000 UART3 base: 0x4000.F000 UART4 base: 0x4001.0000 UART5 base: 0x4001.1000 UART6 base: 0x4001.2000 UART7 base: 0x4001.3000 Offset 0x030

Type R/W, reset 0x0000.0300



Bit/Field	Name	Туре	Reset	Description
31:16	reserved	RO	0x0000	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.

Bit/Field	Name	Туре	Reset	Description
15	CTSEN	R/W	0	Enable Clear To Send
				Value Description
				0 CTS hardware flow control is disabled.
				1 CTS hardware flow control is enabled. Data is only transmitted when the <code>U1CTS</code> signal is asserted.
				This bit is implemented only on UART1 and is reserved for UART0 and UART2.
14	RTSEN	R/W	0	Enable Request to Send
				Value Description
				0 RTS hardware flow control is disabled.
				1 RTS hardware flow control is enabled. Data is only requested (by asserting <code>UIRTS</code>) when the receive FIFO has available entries.
				This bit is implemented only on UART1 and is reserved for UART0 and UART2.
13:12	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
11	RTS	R/W	0	Request to Send
				When RTSEN is clear, the status of this bit is reflected on the U1RTS signal. If RTSEN is set, this bit is ignored on a write and should be ignored on read.
				This bit is implemented only on UART1 and is reserved for UART0 and UART2.
10	DTR	R/W	0	Data Terminal Ready
				This bit sets the state of the U1DTR output.
				This bit is implemented only on UART1 and is reserved for UART0 and UART2.
9	RXE	R/W	1	UART Receive Enable
				Value Description
				0 The receive section of the UART is disabled.
				1 The receive section of the UART is enabled.
				If the UART is disabled in the middle of a receive, it completes the current

February 20, 2013 925

Note:

character before stopping.

To enable reception, the ${\tt UARTEN}$ bit must also be set.

Bit/Field	Name	Туре	Reset	Description
8	TXE	R/W	1	UART Transmit Enable
				Value Description
				0 The transmit section of the UART is disabled.
				1 The transmit section of the UART is enabled.
				If the UART is disabled in the middle of a transmission, it completes the current character before stopping.
				Note: To enable transmission, the UARTEN bit must also be set.
7	LBE	R/W	0	UART Loop Back Enable
				Value Description
				0 Normal operation.
				1 The UnTx path is fed through the UnRx path.
6	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
5	HSE	R/W	0	High-Speed Enable
				Value Description
				The UART is clocked using the system clock divided by 16.
				1 The UART is clocked using the system clock divided by 8.
				Note: System clock used is also dependent on the baud-rate divisor configuration (see page 920) and page 921).
				The state of this bit has no effect on clock generation in ISO 7816 smart card mode (the SMART bit is set).
4	EOT	R/W	0	End of Transmission
				This bit determines the behavior of the ${\tt TXRIS}$ bit in the $\textbf{UARTRIS}$ register.
				Value Description
				O The TXRIS bit is set when the transmit FIFO condition specified in UARTIFLS is met.
				1 The TXRIS bit is set only after all transmitted data, including stop bits, have cleared the serializer.

Bit/Field	Name	Туре	Reset	Description
3	SMART	R/W	0	ISO 7816 Smart Card Support
				Value Description
				0 Normal operation.
				1 The UART operates in Smart Card mode.
				The application must ensure that it sets 8-bit word length (WLEN set to 0x3) and even parity (PEN set to 1, EPS set to 1, SPS set to 0) in UARTLCRH when using ISO 7816 mode.
				In this mode, the value of the STP2 bit in UARTLCRH is ignored and the number of stop bits is forced to 2. Note that the UART does not support automatic retransmission on parity errors. If a parity error is detected on transmission, all further transmit operations are aborted and software must handle retransmission of the affected byte or message.
2	SIRLP	R/W	0	UART SIR Low-Power Mode
				This bit selects the IrDA encoding mode.
				Value Description
				0 Low-level bits are transmitted as an active High pulse with a width of 3/16th of the bit period.
				1 The UART operates in SIR Low-Power mode. Low-level bits are transmitted with a pulse width which is 3 times the period of the IrLPBaud16 input signal, regardless of the selected bit rate.
				Setting this bit uses less power, but might reduce transmission distances. See page 919 for more information.
1	SIREN	R/W	0	UART SIR Enable
				Value Description
				0 Normal operation.
				1 The IrDA SIR block is enabled, and the UART will transmit and receive data using SIR protocol.
0	UARTEN	R/W	0	UART Enable
				Value Description
				0 The UART is disabled.
				1 The UART is enabled.

If the UART is disabled in the middle of transmission or reception, it completes the current character before stopping.

February 20, 2013 927

Register 9: UART Interrupt FIFO Level Select (UARTIFLS), offset 0x034

The **UARTIFLS** register is the interrupt FIFO level select register. You can use this register to define the FIFO level at which the TXRIS and RXRIS bits in the **UARTRIS** register are triggered.

The interrupts are generated based on a transition through a level rather than being based on the level. That is, the interrupts are generated when the fill level progresses through the trigger level. For example, if the receive trigger level is set to the half-way mark, the interrupt is triggered as the module is receiving the 9th character.


Out of reset, the TXIFLSEL and RXIFLSEL bits are configured so that the FIFOs trigger an interrupt at the half-way mark.

UART Interrupt FIFO Level Select (UARTIFLS)

UART0 base: 0x4000.C000 UART1 base: 0x4000.D000 UART2 base: 0x4000.E000 UART3 base: 0x4000.F000 UART4 base: 0x4001.0000 UART5 base: 0x4001.1000 UART6 base: 0x4001.2000 UART7 base: 0x4001.3000

Offset 0x034

Type R/W, reset 0x0000.0012



Bit/Field	Name	Type	Reset	Description
31:6	reserved	RO	0x0000.00	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
5:3	RXIFLSEL	R/W	0x2	UART Receive Interrupt FIFO Level Select

The trigger points for the receive interrupt are as follows:

Value	Description
0x0	RX FIFO ≥ 1/8 full
0x1	RX FIFO ≥ ¼ full
0x2	RX FIFO ≥ ½ full (default)
0x3	RX FIFO ≥ ¾ full
0x4	RX FIFO ≥ ¾ full
0x5-0x7	Reserved

Bit/Field	Name	Type	Reset	Description		
2:0	TXIFLSEL	R/W	0x2		nit Interrupt FIFO Level Select pints for the transmit interrupt are as follows:	
				Value Des	scription	
				0x0 TX	FIFO ≤ % empty	
				0x1 TX	FIFO ≤ ¾ empty	
				0x2 TX	FIFO ≤ ½ empty (default)	
				0x3 TX	FIFO ≤ ¼ empty	
				0x4 TX	FIFO ≤ 1/8 empty	
				0x5-0x7 Res	served	
				inte all d	ne EOT bit in UARTCTL is set (see page 924), the transmit errupt is generated once the FIFO is completely empty and data including stop bits have left the transmit serializer. In scase, the setting of TXIFLSEL is ignored.	

Register 10: UART Interrupt Mask (UARTIM), offset 0x038

The **UARTIM** register is the interrupt mask set/clear register.


On a read, this register gives the current value of the mask on the relevant interrupt. Setting a bit allows the corresponding raw interrupt signal to be routed to the interrupt controller. Clearing a bit prevents the raw interrupt signal from being sent to the interrupt controller.

Note that bits [3:0] are only implemented on UART1. These bits are reserved on UART0 and UART2.

UART Interrupt Mask (UARTIM)

UART0 base: 0x4000.C000 UART1 base: 0x4000.D000 UART2 base: 0x4000.E000 UART3 base: 0x4000.F000 UART4 base: 0x4001.0000 UART5 base: 0x4001.1000 UART6 base: 0x4001.2000 UART7 base: 0x4001.3000 Offset 0x038

Type R/W, reset 0x0000.0000



Bit/Field	Name	Type	Reset	Description
31:13	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
12	9BITIM	R/W	0	9-Bit Mode Interrupt Mask
				Value Description
				O The 9BITRIS interrupt is suppressed and not sent to the interrupt controller.
				An interrupt is sent to the interrupt controller when the 9BITRIS bit in the UARTRIS register is set.
11	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
10	OEIM	R/W	0	UART Overrun Error Interrupt Mask

Value Description

- 0 The OERIS interrupt is suppressed and not sent to the interrupt controller.
- An interrupt is sent to the interrupt controller when the OERIS bit in the UARTRIS register is set.

Bit/Field	Name	Туре	Reset	Description
9	BEIM	R/W	0	UART Break Error Interrupt Mask
				Value Description
				O The BERIS interrupt is suppressed and not sent to the interrupt controller.
				An interrupt is sent to the interrupt controller when the BERIS bit in the UARTRIS register is set.
8	PEIM	R/W	0	UART Parity Error Interrupt Mask
				Value Description
				O The PERIS interrupt is suppressed and not sent to the interrupt controller.
				An interrupt is sent to the interrupt controller when the PERIS bit in the UARTRIS register is set.
7	FEIM	R/W	0	UART Framing Error Interrupt Mask
				Value Description
				O The FERIS interrupt is suppressed and not sent to the interrupt controller.
				An interrupt is sent to the interrupt controller when the FERIS bit in the UARTRIS register is set.
6	RTIM	R/W	0	UART Receive Time-Out Interrupt Mask
				Value Description
				O The RTRIS interrupt is suppressed and not sent to the interrupt controller.
				An interrupt is sent to the interrupt controller when the RTRIS bit in the UARTRIS register is set.
5	TXIM	R/W	0	UART Transmit Interrupt Mask
				Value Description
				O The TXRIS interrupt is suppressed and not sent to the interrupt controller.
				An interrupt is sent to the interrupt controller when the TXRIS bit in the UARTRIS register is set.
4	RXIM	R/W	0	UART Receive Interrupt Mask
				Value Description
				O The RXRIS interrupt is suppressed and not sent to the interrupt controller.
				An interrupt is sent to the interrupt controller when the RXRIS bit in the UARTRIS register is set.

February 20, 2013 931

Bit/Field	Name	Туре	Reset	Description
3	DSRIM	R/W	0	UART Data Set Ready Modem Interrupt Mask
				Value Description
				O The DSRRIS interrupt is suppressed and not sent to the interrupt controller.
				An interrupt is sent to the interrupt controller when the DSRRIS bit in the UARTRIS register is set.
				This bit is implemented only on UART1 and is reserved for UART0 and UART2.
2	DCDIM	R/W	0	UART Data Carrier Detect Modem Interrupt Mask
				Value Description
				O The DCDRIS interrupt is suppressed and not sent to the interrupt controller.
				An interrupt is sent to the interrupt controller when the DCDRIS bit in the UARTRIS register is set.
				This bit is implemented only on UART1 and is reserved for UART0 and UART2.
1	CTSIM	R/W	0	UART Clear to Send Modem Interrupt Mask
				Value Description
				O The CTSRIS interrupt is suppressed and not sent to the interrupt controller.
				An interrupt is sent to the interrupt controller when the CTSRIS bit in the UARTRIS register is set.
				This bit is implemented only on UART1 and is reserved for UART0 and UART2.
0	RIIM	R/W	0	UART Ring Indicator Modem Interrupt Mask
				Value Description
				O The RIRIS interrupt is suppressed and not sent to the interrupt controller.
				An interrupt is sent to the interrupt controller when the RIRIS bit in the UARTRIS register is set.
				This bit is implemented only on UART1 and is reserved for UART0 and

UART2.

Register 11: UART Raw Interrupt Status (UARTRIS), offset 0x03C


The **UARTRIS** register is the raw interrupt status register. On a read, this register gives the current raw status value of the corresponding interrupt. A write has no effect.

Note that bits [3:0] are only implemented on UART1. These bits are reserved on UART0 and UART2.

UART Raw Interrupt Status (UARTRIS)

UART0 base: 0x4000.C000 UART1 base: 0x4000.D000 UART2 base: 0x4000.E000 UART3 base: 0x4000.F000 UART4 base: 0x4001.0000 UART5 base: 0x4001.1000 UART6 base: 0x4001.2000 UART7 base: 0x4001.3000 Offset 0x03C

Type RO, reset 0x0000.0000



Bit/Field	Name	Туре	Reset	Description
31:13	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
12	9BITRIS	RO	0	9-Bit Mode Raw Interrupt Status
				Value Description
				0 No interrupt
				1 A receive address match has occurred.
				This bit is cleared by writing a 1 to the <code>9BITIC</code> bit in the UARTICR register.
11	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
10	OERIS	RO	0	UART Overrun Error Raw Interrupt Status
				Value Description

0

No interrupt

An overrun error has occurred.

This bit is cleared by writing a 1 to the OEIC bit in the **UARTICR** register.

TICR register.
TICD register
TICR register.
TICR register.
TICR register.
ne transmit ned in the lata and flags
: T

This bit is cleared by writing a 1 to the TXIC bit in the **UARTICR** register or by writing data to the transmit FIFO until it becomes greater than the trigger level, if the FIFO is enabled, or by writing a single byte if the FIFO is disabled.

Bit/Field	Name	Туре	Reset	Description
4	RXRIS	RO	0	UART Receive Raw Interrupt Status
				Value Description
				0 No interrupt
				1 The receive FIFO level has passed through the condition defined in the UARTIFLS register.
				This bit is cleared by writing a 1 to the RXIC bit in the UARTICR register or by reading data from the receive FIFO until it becomes less than the trigger level, if the FIFO is enabled, or by reading a single byte if the FIFO is disabled.
3	DSRRIS	RO	0	UART Data Set Ready Modem Raw Interrupt Status
				Value Description
				0 No interrupt
				1 Data Set Ready used for software flow control.
				This bit is cleared by writing a 1 to the DSRIC bit in the UARTICR register.
				This bit is implemented only on UART1 and is reserved for UART0 and UART2.
2	DCDRIS	RO	0	UART Data Carrier Detect Modem Raw Interrupt Status
				Value Description
				0 No interrupt
				1 Data Carrier Detect used for software flow control.
				This bit is cleared by writing a 1 to the DCDIC bit in the UARTICR register.
				This bit is implemented only on UART1 and is reserved for UART0 and UART2.
1	CTSRIS	RO	0	UART Clear to Send Modem Raw Interrupt Status
				Value Description
				0 No interrupt
				1 Clear to Send used for software flow control.
				This bit is cleared by writing a 1 to the CTSIC bit in the UARTICR register.
				This bit is implemented only on UART1 and is reserved for UART0 and UART2.
0	RIRIS	RO	0	UART Ring Indicator Modem Raw Interrupt Status
				Value Description
				0 No interrupt
				1 Ring Indicator used for software flow control.
				This bit is cleared by writing a 1 to the RIIC bit in the UARTICR register.
				This bit is implemented only on UART1 and is reserved for UART0 and UART2.

February 20, 2013 935

Register 12: UART Masked Interrupt Status (UARTMIS), offset 0x040

The **UARTMIS** register is the masked interrupt status register. On a read, this register gives the current masked status value of the corresponding interrupt. A write has no effect.


Note that bits [3:0] are only implemented on UART1. These bits are reserved on UART0 and UART2.

UART Masked Interrupt Status (UARTMIS)

UART0 base: 0x4000.C000 UART1 base: 0x4000.D000 UART2 base: 0x4000.E000 UART3 base: 0x4000.F000 UART4 base: 0x4001.0000 UART5 base: 0x4001.1000 UART6 base: 0x4001.2000 UART7 base: 0x4001.3000

Offset 0x040

Type RO, reset 0x0000.0000



Bit/Field	Name	Type	Reset	Description
31:13	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
12	9BITMIS	RO	0	9-Bit Mode Masked Interrupt Status
				Value Description
				O An interrupt has not occurred or is masked.
				An unmasked interrupt was signaled due to a receive address match.
				This bit is cleared by writing a 1 to the <code>9BITIC</code> bit in the UARTICR register.
11	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
10	OEMIS	RO	0	UART Overrun Error Masked Interrupt Status
				Value Description

- 0 An interrupt has not occurred or is masked.
- 1 An unmasked interrupt was signaled due to an overrun error.

This bit is cleared by writing a 1 to the OEIC bit in the **UARTICR** register.

Bit/Field	Name	Type	Reset	Description
9	BEMIS	RO	0	UART Break Error Masked Interrupt Status
				Value Description O An interrupt has not occurred or is masked. An unmasked interrupt was signaled due to a break error.
				This bit is cleared by writing a 1 to the ${\tt BEIC}$ bit in the $\textbf{UARTICR}$ register.
8	PEMIS	RO	0	UART Parity Error Masked Interrupt Status
				Value Description O An interrupt has not occurred or is masked. 1 An unmasked interrupt was signaled due to a parity error. This bit is cleared by writing a 1 to the PEIC bit in the UARTICR register.
7	FEMIS	RO	0	UART Framing Error Masked Interrupt Status
,	LIMIC		o o	Value Description O An interrupt has not occurred or is masked. An unmasked interrupt was signaled due to a framing error. This bit is cleared by writing a 1 to the FEIC bit in the UARTICR register.
6	RTMIS	RO	0	UART Receive Time-Out Masked Interrupt Status Value Description O An interrupt has not occurred or is masked. 1 An unmasked interrupt was signaled due to a receive time out. This bit is cleared by writing a 1 to the RTIC bit in the UARTICR register.
5	TXMIS	RO	0	UART Transmit Masked Interrupt Status
				 Value Description An interrupt has not occurred or is masked. An unmasked interrupt was signaled due to passing through the specified transmit FIFO level (if the EOT bit is clear) or due to the transmission of the last data bit (if the EOT bit is set).

This bit is cleared by writing a 1 to the <code>TXIC</code> bit in the **UARTICR** register or by writing data to the transmit FIFO until it becomes greater than the trigger level, if the FIFO is enabled, or by writing a single byte if the FIFO is disabled.

February 20, 2013 937

Bit/Field	Name	Туре	Reset	Description
4	RXMIS	RO	0	UART Receive Masked Interrupt Status
				Value Description
				O An interrupt has not occurred or is masked.
				An unmasked interrupt was signaled due to passing through the specified receive FIFO level.
				This bit is cleared by writing a 1 to the RXIC bit in the UARTICR register or by reading data from the receive FIFO until it becomes less than the trigger level, if the FIFO is enabled, or by reading a single byte if the FIFO is disabled.
3	DSRMIS	RO	0	UART Data Set Ready Modem Masked Interrupt Status
				Value Description
				O An interrupt has not occurred or is masked.
				1 An unmasked interrupt was signaled due to Data Set Ready.
				This bit is cleared by writing a 1 to the DSRIC bit in the UARTICR register.
				This bit is implemented only on UART1 and is reserved for UART0 and UART2.
2	DCDMIS	RO	0	UART Data Carrier Detect Modem Masked Interrupt Status
				Value Description
				O An interrupt has not occurred or is masked.
				1 An unmasked interrupt was signaled due to Data Carrier Detect.
				This bit is cleared by writing a 1 to the DCDIC bit in the UARTICR register.
				This bit is implemented only on UART1 and is reserved for UART0 and UART2.
1	CTSMIS	RO	0	UART Clear to Send Modem Masked Interrupt Status
				Value Description
				O An interrupt has not occurred or is masked.
				1 An unmasked interrupt was signaled due to Clear to Send.
				This bit is cleared by writing a 1 to the CTSIC bit in the UARTICR register.
				This bit is implemented only on UART1 and is reserved for UART0 and UART2.
0	RIMIS	RO	0	UART Ring Indicator Modem Masked Interrupt Status
				Value Description
				O An interrupt has not occurred or is masked.
				1 An unmasked interrupt was signaled due to Ring Indicator.
				This bit is cleared by writing a 1 to the RIIC bit in the UARTICR register.
				This bit is implemented only on UART1 and is reserved for UART0 and UART2.

Register 13: UART Interrupt Clear (UARTICR), offset 0x044

The **UARTICR** register is the interrupt clear register. On a write of 1, the corresponding interrupt (both raw interrupt and masked interrupt, if enabled) is cleared. A write of 0 has no effect.

Note that bits [3:0] are only implemented on UART1. These bits are reserved on UART0 and UART2.

UART Interrupt Clear (UARTICR)

UART0 base: 0x4000.C000 UART1 base: 0x4000.D000 UART2 base: 0x4000.E000 UART3 base: 0x4000.F000 UART4 base: 0x4001.0000 UART5 base: 0x4001.1000 UART6 base: 0x4001.2000 UART7 base: 0x4001.3000 Offset 0x044

Type W1C, reset 0x0000.0000

_	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16
		1 1		1	, , ,			rese	rved) 		'	
Type Reset	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0
_	15	14	13	12	11	10	9	8	7	6	5	4	3	2	1	0
		reserved		9BITIC	reserved	OEIC	BEIC	PEIC	FEIC	RTIC	TXIC	RXIC	DSRMIC	DCDMIC	CTSMIC	RIMIC
Type Reset	RO 0	RO 0	RO 0	R/W 0	RO 0	W1C 0	W1C	W1C	W1C 0	W1C	W1C	W1C 0	W1C 0	W1C 0	W1C 0	W1C 0

Bit/Field	Name	Туре	Reset	Description
31:13	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
12	9BITIC	R/W	0	9-Bit Mode Interrupt Clear
				Writing a 1 to this bit clears the <code>9BITRIS</code> bit in the UARTRIS register and the <code>9BITMIS</code> bit in the UARTMIS register.
11	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
10	OEIC	W1C	0	Overrun Error Interrupt Clear
				Writing a 1 to this bit clears the OERIS bit in the UARTRIS register and the OEMIS bit in the UARTMIS register.
9	BEIC	W1C	0	Break Error Interrupt Clear
				Writing a 1 to this bit clears the BERIS bit in the UARTRIS register and the BEMIS bit in the UARTMIS register.
8	PEIC	W1C	0	Parity Error Interrupt Clear
				Writing a 1 to this bit clears the PERIS bit in the UARTRIS register and the PEMIS bit in the UARTMIS register.
7	FEIC	W1C	0	Framing Error Interrupt Clear
				Writing a 1 to this bit clears the FERIS bit in the UARTRIS register and the FEMIS bit in the UARTMIS register.

Bit/Field	Name	Туре	Reset	Description
6	RTIC	W1C	0	Receive Time-Out Interrupt Clear Writing a 1 to this bit clears the RTRIS bit in the UARTRIS register and the RTMIS bit in the UARTMIS register.
5	TXIC	W1C	0	Transmit Interrupt Clear Writing a 1 to this bit clears the TXRIS bit in the UARTRIS register and the TXMIS bit in the UARTMIS register.
4	RXIC	W1C	0	Receive Interrupt Clear Writing a 1 to this bit clears the RXRIS bit in the UARTRIS register and the RXMIS bit in the UARTMIS register.
3	DSRMIC	W1C	0	UART Data Set Ready Modem Interrupt Clear Writing a 1 to this bit clears the DSRRIS bit in the UARTRIS register and the DSRMIS bit in the UARTMIS register. This bit is implemented only on UART1 and is reserved for UART0 and UART2.
2	DCDMIC	W1C	0	UART Data Carrier Detect Modem Interrupt Clear Writing a 1 to this bit clears the DCDRIS bit in the UARTRIS register and the DCDMIS bit in the UARTMIS register. This bit is implemented only on UART1 and is reserved for UART0 and UART2.
1	CTSMIC	W1C	0	UART Clear to Send Modem Interrupt Clear Writing a 1 to this bit clears the CTSRIS bit in the UARTRIS register and the CTSMIS bit in the UARTMIS register. This bit is implemented only on UART1 and is reserved for UART0 and UART2.
0	RIMIC	W1C	0	UART Ring Indicator Modem Interrupt Clear Writing a 1 to this bit clears the RIRIS bit in the UARTRIS register and the RIMIS bit in the UARTMIS register. This bit is implemented only on UART1 and is reserved for UART0 and UART2.


Register 14: UART DMA Control (UARTDMACTL), offset 0x048

The **UARTDMACTL** register is the DMA control register.

UART DMA Control (UARTDMACTL)

UART0 base: 0x4000.C000 UART1 base: 0x4000.D000 UART2 base: 0x4000.E000 UART3 base: 0x4000.F000 UART4 base: 0x4001.0000 UART5 base: 0x4001.1000
UART6 base: 0x4001.2000
UART7 base: 0x4001.3000
Offset 0x048

Type R/W, reset 0x0000.0000



Bit/Field	Name	Туре	Reset	Description
31:3	reserved	RO	0x00000.000	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
2	DMAERR	R/W	0	DMA on Error
				Value Description
				0 μDMA receive requests are unaffected when a receive error occurs.
				1 μDMA receive requests are automatically disabled when a receive error occurs.
1	TXDMAE	R/W	0	Transmit DMA Enable
				Value Description
				0 μDMA for the transmit FIFO is disabled.
				1 μDMA for the transmit FIFO is enabled.
0	RXDMAE	R/W	0	Receive DMA Enable
				Value Description
				0 μDMA for the receive FIFO is disabled.
				4 DMA for the marker FIFO is excelled

 μDMA for the receive FIFO is enabled.


Register 15: UART 9-Bit Self Address (UART9BITADDR), offset 0x0A4

The **UART9BITADDR** register is used to write the specific address that should be matched with the receiving byte when the 9-bit Address Mask (UART9BITAMASK) is set to 0xFF. This register is used in conjunction with **UART9BITAMASK** to form a match for address-byte received.

UART 9-Bit Self Address (UART9BITADDR)

UART0 base: 0x4000.C000 UART1 base: 0x4000.D000 UART2 base: 0x4000.E000 UART3 base: 0x4000.F000 UART4 base: 0x4001.0000 UART5 base: 0x4001.1000 UART6 base: 0x4001.2000 UART7 base: 0x4001.3000 Offset 0x0A4

Type R/W, reset 0x0000.0000



Bit/Field	Name	Type	Reset	Description
31:16	reserved	RO	0x0000	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
15	9BITEN	R/W	0	Enable 9-Bit Mode
				Value Description
				0 9-bit mode is disabled.
				1 9-bit mode is enabled.
14:8	reserved	RO	0x0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
7:0	ADDR	R/W	0x00	Self Address for 9-Bit Mode
				This field contains the address that should be matched when UART9BITAMASK is 0xFF.

Register 16: UART 9-Bit Self Address Mask (UART9BITAMASK), offset 0x0A8


The **UART9BITAMASK** register is used to enable the address mask for 9-bit mode. The address bits are masked to create a set of addresses to be matched with the received address byte.

UART 9-Bit Self Address Mask (UART9BITAMASK)

UART0 base: 0x4000.C000 UART1 base: 0x4000.D000 UART2 base: 0x4000.E000 UART3 base: 0x4000.F000 UART4 base: 0x4001.0000 UART5 base: 0x4001.1000 UART6 base: 0x4001.2000 UART7 base: 0x4001.3000

Offset 0x0A8

Type R/W, reset 0x0000.00FF



Bit/Field	Name	Туре	Reset	Description
31:8	reserved	RO	0x00	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
7:0	MVCK	DAM	OVEE	Solf Address Mask for Q Bit Mode

This field contains the address mask that creates a set of addresses that should be matched.


Register 17: UART Peripheral Properties (UARTPP), offset 0xFC0

The **UARTPP** register provides information regarding the properties of the UART module.

UART Peripheral Properties (UARTPP)

UART0 base: 0x4000.C000 UART1 base: 0x4000.D000 UART2 base: 0x4000.E000 UART3 base: 0x4000.F000 UART4 base: 0x4001.0000 UART5 base: 0x4001.1000 UART6 base: 0x4001.2000 UART7 base: 0x4001.3000 Offset 0xFC0

Type RO, reset 0x0000.0003



Bit/Field	Name	Type	Reset	Description
31:2	reserved	RO	0x0000.000	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
1	NB	RO	0x1	9-Bit Support
				Value Description
				The UART module does not provide support for the transmission of 9-bit data for RS-485 support.
				1 The UART module provides support for the transmission of 9-bit data for RS-485 support.
0	SC	RO	0x1	Smart Card Support

Value Description

The UART module does not provide smart card support.

The UART module provides smart card support.

Register 18: UART Clock Configuration (UARTCC), offset 0xFC8


The **UARTCC** register controls the baud clock source for the UART module. For more information, see the section called "Communication Clock Sources" on page 226.

Note: If the PIOSC is used for the UART baud clock, the system clock frequency must be at least 9 MHz in Run mode.

UART Clock Configuration (UARTCC)

UART0 base: 0x4000.C000 UART1 base: 0x4000.D000 UART2 base: 0x4000.E000 UART3 base: 0x4000.F000 UART4 base: 0x4001.0000 UART5 base: 0x4001.1000 UART6 base: 0x4001.2000 UART7 base: 0x4001.3000 Offset 0xFC8

Type R/W, reset 0x0000.0000



Bit/Field	Name	туре	Reset	Description
31:4	reserved	RO	0x0000.000	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
3:0	cs	R/W	0	UART Baud Clock Source

The following table specifies the source that generates for the UART baud clock:

Value Description

0x0 System clock (based on clock source and divisor factor)

0x1-0x4 reserved 0x5 PIOSC 0x5-0xF Reserved

Register 19: UART Peripheral Identification 4 (UARTPeriphID4), offset 0xFD0

The **UARTPeriphIDn** registers are hard-coded and the fields within the registers determine the reset values.


UART Peripheral Identification 4 (UARTPeriphID4)

UART0 base: 0x4000.C000 UART1 base: 0x4000.D000 UART2 base: 0x4000.E000 UART3 base: 0x4000.F000 UART4 base: 0x4001.0000 UART5 base: 0x4001.1000 UART5 base: 0x4001.2000

UART7 base: 0x4001.3000

Offset 0xFD0

Type RO, reset 0x0000.0000



Bit/Field	Name	Туре	Reset	Description
31:8	reserved	RO	0x0000.00	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
7:0	PID4	RO	0x00	UART Peripheral ID Register [7:0]

Register 20: UART Peripheral Identification 5 (UARTPeriphID5), offset 0xFD4


The **UARTPeriphIDn** registers are hard-coded and the fields within the registers determine the reset values.

UART Peripheral Identification 5 (UARTPeriphID5)

UART0 base: 0x4000.C000
UART1 base: 0x4000.D000
UART2 base: 0x4000.E000
UART3 base: 0x4000.F000
UART4 base: 0x4001.0000
UART5 base: 0x4001.1000
UART6 base: 0x4001.2000
UART7 base: 0x4001.3000

Offset 0xFD4

Type RO, reset 0x0000.0000



Bit/Field	Name	Туре	Reset	Description
31:8	reserved	RO	0x0000.00	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
7:0	PID5	RO	0x00	UART Peripheral ID Register [15:8]

Register 21: UART Peripheral Identification 6 (UARTPeriphID6), offset 0xFD8


The **UARTPeriphIDn** registers are hard-coded and the fields within the registers determine the reset values.

UART Peripheral Identification 6 (UARTPeriphID6)

UART0 base: 0x4000.C000 UART1 base: 0x4000.D000 UART2 base: 0x4000.E000 UART3 base: 0x4000.F000 UART4 base: 0x4001.0000 UART5 base: 0x4001.1000 UART6 base: 0x4001.2000

UART7 base: 0x4001.3000 Offset 0xFD8

Type RO, reset 0x0000.0000



Bit/Field	Name	Type	Reset	Description
31:8	reserved	RO	0x0000.00	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
7:0	PID6	RO	0x00	UART Peripheral ID Register [23:16]

Register 22: UART Peripheral Identification 7 (UARTPeriphID7), offset 0xFDC


The **UARTPeriphIDn** registers are hard-coded and the fields within the registers determine the reset values.

UART Peripheral Identification 7 (UARTPeriphID7)

UART0 base: 0x4000.C000
UART1 base: 0x4000.D000
UART2 base: 0x4000.E000
UART3 base: 0x4000.F000
UART4 base: 0x4001.0000
UART5 base: 0x4001.1000
UART6 base: 0x4001.2000
UART7 base: 0x4001.3000

Offset 0xFDC

Type RO, reset 0x0000.0000



Bit/Field	Name	Туре	Reset	Description
31:8	reserved	RO	0x0000.00	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
7:0	PID7	RO	0x00	UART Peripheral ID Register [31:24]

Register 23: UART Peripheral Identification 0 (UARTPeriphID0), offset 0xFE0


The **UARTPeriphIDn** registers are hard-coded and the fields within the registers determine the reset values.

UART Peripheral Identification 0 (UARTPeriphID0)

UART0 base: 0x4000.C000 UART1 base: 0x4000.D000 UART2 base: 0x4000.E000 UART3 base: 0x4000.F000 UART4 base: 0x4001.0000 UART5 base: 0x4001.1000 UART6 base: 0x4001.2000 UART7 base: 0x4001.3000

Offset 0xFE0

Type RO, reset 0x0000.0060



Bit/Field	Name	Туре	Reset	Description
31:8	reserved	RO	0x0000.00	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
7:0	PID0	RO	0x60	UART Peripheral ID Register [7:0]

Register 24: UART Peripheral Identification 1 (UARTPeriphID1), offset 0xFE4


The **UARTPeriphIDn** registers are hard-coded and the fields within the registers determine the reset values.

UART Peripheral Identification 1 (UARTPeriphID1)

UART0 base: 0x4000.C000
UART1 base: 0x4000.D000
UART2 base: 0x4000.E000
UART3 base: 0x4000.F000
UART4 base: 0x4001.0000
UART5 base: 0x4001.1000
UART6 base: 0x4001.2000
UART7 base: 0x4001.3000

Offset 0xFE4

Type RO, reset 0x0000.0000



Bit/Field	Name	Type	Reset	Description
31:8	reserved	RO	0x0000.00	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
7:0	PID1	RO	0x00	UART Peripheral ID Register [15:8]

Register 25: UART Peripheral Identification 2 (UARTPeriphID2), offset 0xFE8


The **UARTPeriphIDn** registers are hard-coded and the fields within the registers determine the reset values.

UART Peripheral Identification 2 (UARTPeriphID2)

UART0 base: 0x4000.C000 UART1 base: 0x4000.D000 UART2 base: 0x4000.E000 UART3 base: 0x4000.F000 UART4 base: 0x4001.0000 UART5 base: 0x4001.1000 UART6 base: 0x4001.2000 UART7 base: 0x4001.3000

Offset 0xFE8

Type RO, reset 0x0000.0018



Bit/Field	Name	Туре	Reset	Description
31:8	reserved	RO	0x0000.00	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
7:0	PID2	RO	0x18	UART Peripheral ID Register [23:16]

Register 26: UART Peripheral Identification 3 (UARTPeriphID3), offset 0xFEC


The **UARTPeriphIDn** registers are hard-coded and the fields within the registers determine the reset values.

UART Peripheral Identification 3 (UARTPeriphID3)

UART0 base: 0x4000.C000
UART1 base: 0x4000.D000
UART2 base: 0x4000.E000
UART3 base: 0x4000.F000
UART4 base: 0x4001.0000
UART5 base: 0x4001.1000
UART6 base: 0x4001.2000
UART7 base: 0x4001.3000

Offset 0xFEC

Type RO, reset 0x0000.0001



Bit/Field	d Name	Type	Reset	Description
31:8	reserved	RO	0x0000.00	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
7:0	PID3	RO	0x01	UART Peripheral ID Register [31:24]

Register 27: UART PrimeCell Identification 0 (UARTPCellID0), offset 0xFF0


The **UARTPCellIDn** registers are hard-coded and the fields within the registers determine the reset values.

UART PrimeCell Identification 0 (UARTPCellID0)

UART0 base: 0x4000.C000 UART1 base: 0x4000.D000 UART2 base: 0x4000.E000 UART3 base: 0x4000.F000 UART4 base: 0x4001.0000 UART5 base: 0x4001.1000 UART6 base: 0x4001.2000 UART7 base: 0x4001.3000

Offset 0xFF0

Type RO, reset 0x0000.000D



Bit/Field	Name	Туре	Reset	Description
31:8	reserved	RO	0x0000.00	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
7:0	CID0	RO	0x0D	UART PrimeCell ID Register [7:0]

Register 28: UART PrimeCell Identification 1 (UARTPCellID1), offset 0xFF4


The **UARTPCellIDn** registers are hard-coded and the fields within the registers determine the reset values.

UART PrimeCell Identification 1 (UARTPCellID1)

UART0 base: 0x4000.C000 UART1 base: 0x4000.D000 UART2 base: 0x4000.E000 UART3 base: 0x4000.F000 UART4 base: 0x4001.0000 UART5 base: 0x4001.1000 UART6 base: 0x4001.2000 UART7 base: 0x4001.3000

Offset 0xFF4

Type RO, reset 0x0000.00F0



Bit/Field	Name	Туре	Reset	Description
31:8	reserved	RO	0x0000.00	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
7:0	CID1	RO	0xF0	UART PrimeCell ID Register [15:8]

Register 29: UART PrimeCell Identification 2 (UARTPCellID2), offset 0xFF8


The **UARTPCellIDn** registers are hard-coded and the fields within the registers determine the reset values.

UART PrimeCell Identification 2 (UARTPCellID2)

UART0 base: 0x4000.C000 UART1 base: 0x4000.D000 UART2 base: 0x4000.E000 UART3 base: 0x4000.F000 UART4 base: 0x4001.0000 UART5 base: 0x4001.1000 UART6 base: 0x4001.2000 UART7 base: 0x4001.3000

Offset 0xFF8

Type RO, reset 0x0000.0005



Bit/Field	Name	Туре	Reset	Description
31:8	reserved	RO	0x0000.00	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
7:0	CID2	RO	0x05	UART PrimeCell ID Register [23:16]

Register 30: UART PrimeCell Identification 3 (UARTPCellID3), offset 0xFFC


The **UARTPCellIDn** registers are hard-coded and the fields within the registers determine the reset values.

UART PrimeCell Identification 3 (UARTPCellID3)

UART0 base: 0x4000.C000 UART1 base: 0x4000.D000 UART2 base: 0x4000.E000 UART3 base: 0x4000.F000 UART4 base: 0x4001.0000 UART5 base: 0x4001.1000 UART6 base: 0x4001.2000 UART7 base: 0x4001.3000

Offset 0xFFC

Type RO, reset 0x0000.00B1



Bit/Field	Name	Туре	Reset	Description
31:8	reserved	RO	0x0000.00	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
7:0	CID3	RO	0xB1	UART PrimeCell ID Register [31:24]

15 Synchronous Serial Interface (SSI)


The Stellaris[®] microcontroller includes four Synchronous Serial Interface (SSI) modules. Each SSI module is a master or slave interface for synchronous serial communication with peripheral devices that have either Freescale SPI, MICROWIRE, or Texas Instruments synchronous serial interfaces.

The Stellaris LM4F232H5QC SSI modules have the following features:

- Programmable interface operation for Freescale SPI, MICROWIRE, or Texas Instruments synchronous serial interfaces
- Master or slave operation
- Programmable clock bit rate and prescaler
- Separate transmit and receive FIFOs, each 16 bits wide and 8 locations deep
- Programmable data frame size from 4 to 16 bits
- Internal loopback test mode for diagnostic/debug testing
- Standard FIFO-based interrupts and End-of-Transmission interrupt
- Efficient transfers using Micro Direct Memory Access Controller (μDMA)
 - Separate channels for transmit and receive
 - Receive single request asserted when data is in the FIFO; burst request asserted when FIFO contains 4 entries
 - Transmit single request asserted when there is space in the FIFO; burst request asserted when four or more entries are available to be written in the FIFO

15.1 Block Diagram

Figure 15-1. SSI Module Block Diagram



15.2 Signal Description

The following table lists the external signals of the SSI module and describes the function of each. Most SSI signals are alternate functions for some GPIO signals and default to be GPIO signals at reset. The exceptions to this rule are the SSIOClk, SSIOFSS, SSIORX, and SSIOTX pins, which default to the SSI function. The "Pin Mux/Pin Assignment" column in the following table lists the possible GPIO pin placements for the SSI signals. The AFSEL bit in the **GPIO Alternate Function Select (GPIOAFSEL)** register (page 670) should be set to choose the SSI function. The number in parentheses is the encoding that must be programmed into the PMCn field in the **GPIO Port Control (GPIOPCTL)** register (page 688) to assign the SSI signal to the specified GPIO port pin. For more information on configuring GPIOs, see "General-Purpose Input/Outputs (GPIOs)" on page 646.

Table 15-1. SSI Signals (100LQFP)

Pin Name	Pin Number	Pin Mux / Pin Assignment	Pin Type	Buffer Type ^a	Description
SSI0Clk	28	PA2 (2)	I/O	TTL	SSI module 0 clock
SSI0Fss	29	PA3 (2)	I/O	TTL	SSI module 0 frame signal
SSI0Rx	30	PA4 (2)	1	TTL	SSI module 0 receive
SSI0Tx	31	PA5 (2)	0	TTL	SSI module 0 transmit
SSI1Clk	1 42	PD0 (2) PF2 (2)	I/O	TTL	SSI module 1 clock.
SSI1Fss	2 43	PD1 (2) PF3 (2)	I/O	TTL	SSI module 1 frame signal.
SSI1Rx	3 40	PD2 (2) PF0 (2)	I	TTL	SSI module 1 receive.
SSI1Tx	4 41	PD3 (2) PF1 (2)	0	TTL	SSI module 1 transmit.
SSI2Clk	79 92	PH4 (2) PB4 (2)	I/O	TTL	SSI module 2 clock.
SSI2Fss	78 91	PH5 (2) PB5 (2)	I/O	TTL	SSI module 2 frame signal.
SSI2Rx	77	PH6 (2)	I	TTL	SSI module 2 receive.
SSI2Tx	76	PH7 (2)	0	TTL	SSI module 2 transmit.
SSI3Clk	1 16 49	PD0 (1) PH0 (2) PK0 (2)	I/O	TTL	SSI module 3 clock.
SSI3Fss	2 17 48	PD1 (1) PH1 (2) PK1 (2)	I/O	TTL	SSI module 3 frame signal.
SSI3Rx	3 18 47	PD2 (1) PH2 (2) PK2 (2)	I	TTL	SSI module 3 receive.
SSI3Tx	4 19 46	PD3 (1) PH3 (2) PK3 (2)	0	TTL	SSI module 3 transmit.

a. The TTL designation indicates the pin has TTL-compatible voltage levels.

15.3 Functional Description

The SSI performs serial-to-parallel conversion on data received from a peripheral device. The CPU accesses data, control, and status information. The transmit and receive paths are buffered with internal FIFO memories allowing up to eight 16-bit values to be stored independently in both transmit and receive modes. The SSI also supports the μ DMA interface. The transmit and receive FIFOs can be programmed as destination/source addresses in the μ DMA module. μ DMA operation is enabled by setting the appropriate bit(s) in the **SSIDMACTL** register (see page 988).

15.3.1 Bit Rate Generation

The SSI includes a programmable bit rate clock divider and prescaler to generate the serial output clock. Bit rates are supported to 2 MHz and higher, although maximum bit rate is determined by peripheral devices.

The serial bit rate is derived by dividing down the input clock (SysClk). The clock is first divided by an even prescale value CPSDVSR from 2 to 254, which is programmed in the SSI Clock Prescale

(SSICPSR) register (see page 981). The clock is further divided by a value from 1 to 256, which is 1 + SCR, where SCR is the value programmed in the SSI Control 0 (SSICR0) register (see page 974).

The frequency of the output clock SSIClk is defined by:

```
SSIClk = SysClk / (CPSDVSR * (1 + SCR))
```

Note: The PIOSC is used as the source for the SSIClk when the CS field in the SSI Clock Configuration (SSICC) register is configured to 0x5. For master mode, the system clock or the PIOSC must be at least two times faster than the SSIClk, with the restriction that SSIClk cannot be faster than 25 MHz. For slave mode, the system clock or the PIOSC must be at least 6 times faster than the SSIClk.

See "Synchronous Serial Interface (SSI)" on page 1407 to view SSI timing parameters.

15.3.2 FIFO Operation

15.3.2.1 Transmit FIFO

The common transmit FIFO is a 16-bit wide, 8-locations deep, first-in, first-out memory buffer. The CPU writes data to the FIFO by writing the **SSI Data (SSIDR)** register (see page 978), and data is stored in the FIFO until it is read out by the transmission logic.

When configured as a master or a slave, parallel data is written into the transmit FIFO prior to serial conversion and transmission to the attached slave or master, respectively, through the SSITX pin.

In slave mode, the SSI transmits data each time the master initiates a transaction. If the transmit FIFO is empty and the master initiates, the slave transmits the 8th most recent value in the transmit FIFO. If less than 8 values have been written to the transmit FIFO since the SSI module clock was enabled using the \mathbb{R}^n bit in the **RCGCSSI** register, then 0 is transmitted. Care should be taken to ensure that valid data is in the FIFO as needed. The SSI can be configured to generate an interrupt or a μDMA request when the FIFO is empty.

15.3.2.2 Receive FIFO

The common receive FIFO is a 16-bit wide, 8-locations deep, first-in, first-out memory buffer. Received data from the serial interface is stored in the buffer until read out by the CPU, which accesses the read FIFO by reading the **SSIDR** register.

When configured as a master or slave, serial data received through the SSIRx pin is registered prior to parallel loading into the attached slave or master receive FIFO, respectively.

15.3.3 Interrupts

The SSI can generate interrupts when the following conditions are observed:

- Transmit FIFO service (when the transmit FIFO is half full or less)
- Receive FIFO service (when the receive FIFO is half full or more)
- Receive FIFO time-out
- Receive FIFO overrun
- End of transmission
- Receive DMA transfer complete

■ Transmit DMA transfer complete

All of the interrupt events are ORed together before being sent to the interrupt controller, so the SSI generates a single interrupt request to the controller regardless of the number of active interrupts. Each of the four individual maskable interrupts can be masked by clearing the appropriate bit in the **SSI Interrupt Mask (SSIIM)** register (see page 982). Setting the appropriate mask bit enables the interrupt.

The individual outputs, along with a combined interrupt output, allow use of either a global interrupt service routine or modular device drivers to handle interrupts. The transmit and receive dynamic dataflow interrupts have been separated from the status interrupts so that data can be read or written in response to the FIFO trigger levels. The status of the individual interrupt sources can be read from the SSI Raw Interrupt Status (SSIRIS) and SSI Masked Interrupt Status (SSIMIS) registers (see page 983 and page 985, respectively).

The receive FIFO has a time-out period that is 32 periods at the rate of SSIClk (whether or not SSIClk is currently active) and is started when the RX FIFO goes from EMPTY to not-EMPTY. If the RX FIFO is emptied before 32 clocks have passed, the time-out period is reset. As a result, the ISR should clear the Receive FIFO Time-out Interrupt just after reading out the RX FIFO by writing a 1 to the RTIC bit in the SSI Interrupt Clear (SSIICR) register. The interrupt should not be cleared so late that the ISR returns before the interrupt is actually cleared, or the ISR may be re-activated unnecessarily.

The End-of-Transmission (EOT) interrupt indicates that the data has been transmitted completely and is only valid for Master mode devices/operations. This interrupt can be used to indicate when it is safe to turn off the SSI module clock or enter sleep mode. In addition, because transmitted data and received data complete at exactly the same time, the interrupt can also indicate that read data is ready immediately, without waiting for the receive FIFO time-out period to complete.

Note: In Freescale SPI mode only, a condition can be created where an EOT interrupt is generated for every byte transferred even if the FIFO is full. If the EOT bit has been set to 0 in an integrated slave SSI and the μDMA has been configured to transfer data from this SSI to a Master SSI on the device using external loopback, an EOT interrupt is generated by the SSI slave for every byte even if the FIFO is full.

15.3.4 Frame Formats

Each data frame is between 4 and 16 bits long depending on the size of data programmed and is transmitted starting with the MSB. There are three basic frame types that can be selected by programming the FRF bit in the **SSICR0** register:

- Texas Instruments synchronous serial
- Freescale SPI
- MICROWIRE

For all three formats, the serial clock (SSIClk) is held inactive while the SSI is idle, and SSIClk transitions at the programmed frequency only during active transmission or reception of data. The idle state of SSIClk is utilized to provide a receive timeout indication that occurs when the receive FIFO still contains data after a timeout period.

For Freescale SPI and MICROWIRE frame formats, the serial frame (SSIFss) pin is active Low, and is asserted (pulled down) during the entire transmission of the frame.

For Texas Instruments synchronous serial frame format, the SSIFss pin is pulsed for one serial clock period starting at its rising edge, prior to the transmission of each frame. For this frame format, both the SSI and the off-chip slave device drive their output data on the rising edge of SSIClk and latch data from the other device on the falling edge.

Unlike the full-duplex transmission of the other two frame formats, the MICROWIRE format uses a special master-slave messaging technique which operates at half-duplex. In this mode, when a frame begins, an 8-bit control message is transmitted to the off-chip slave. During this transmit, no incoming data is received by the SSI. After the message has been sent, the off-chip slave decodes it and, after waiting one serial clock after the last bit of the 8-bit control message has been sent, responds with the requested data. The returned data can be 4 to 16 bits in length, making the total frame length anywhere from 13 to 25 bits.

15.3.4.1 Texas Instruments Synchronous Serial Frame Format

Figure 15-2 on page 963 shows the Texas Instruments synchronous serial frame format for a single transmitted frame.




Figure 15-2. TI Synchronous Serial Frame Format (Single Transfer)

In this mode, SSIClk and SSIFSS are forced Low, and the transmit data line SSITx is tristated whenever the SSI is idle. Once the bottom entry of the transmit FIFO contains data, SSIFSS is pulsed High for one SSIClk period. The value to be transmitted is also transferred from the transmit FIFO to the serial shift register of the transmit logic. On the next rising edge of SSIClk, the MSB of the 4 to 16-bit data frame is shifted out on the SSITx pin. Likewise, the MSB of the received data is shifted onto the SSIRx pin by the off-chip serial slave device.

Both the SSI and the off-chip serial slave device then clock each data bit into their serial shifter on each falling edge of SSIClk. The received data is transferred from the serial shifter to the receive FIFO on the first rising edge of SSIClk after the LSB has been latched.

Figure 15-3 on page 964 shows the Texas Instruments synchronous serial frame format when back-to-back frames are transmitted.

SSICIK

SSIFss

SSITx/SSIRx

MSB

4 to 16 bits

Figure 15-3. TI Synchronous Serial Frame Format (Continuous Transfer)

15.3.4.2 Freescale SPI Frame Format

The Freescale SPI interface is a four-wire interface where the SSIFss signal behaves as a slave select. The main feature of the Freescale SPI format is that the inactive state and phase of the SSIClk signal are programmable through the SPO and SPH bits in the **SSISCR0** control register.

SPO Clock Polarity Bit

When the SPO clock polarity control bit is clear, it produces a steady state Low value on the SSIC1k pin. If the SPO bit is set, a steady state High value is placed on the SSIC1k pin when data is not being transferred.

SPH Phase Control Bit

The SPH phase control bit selects the clock edge that captures data and allows it to change state. The state of this bit has the most impact on the first bit transmitted by either allowing or not allowing a clock transition before the first data capture edge. When the SPH phase control bit is clear, data is captured on the first clock edge transition. If the SPH bit is set, data is captured on the second clock edge transition.

15.3.4.3 Freescale SPI Frame Format with SPO=0 and SPH=0

Single and continuous transmission signal sequences for Freescale SPI format with SPO=0 and SPH=0 are shown in Figure 15-4 on page 964 and Figure 15-5 on page 965.




Figure 15-4. Freescale SPI Format (Single Transfer) with SPO=0 and SPH=0

964 February 20, 2013




Figure 15-5. Freescale SPI Format (Continuous Transfer) with SPO=0 and SPH=0

In this configuration, during idle periods:

- SSIClk is forced Low
- SSIFss is forced High
- The transmit data line SSITx is arbitrarily forced Low
- When the SSI is configured as a master, it enables the SSIClk pad
- When the SSI is configured as a slave, it disables the SSIClk pad

If the SSI is enabled and valid data is in the transmit FIFO, the start of transmission is signified by the SSIFss master signal being driven Low, causing slave data to be enabled onto the SSIRx input line of the master. The master SSITx output pad is enabled.

One half SSIC1k period later, valid master data is transferred to the SSITx pin. Once both the master and slave data have been set, the SSIC1k master clock pin goes High after one additional half SSIC1k period.

The data is now captured on the rising and propagated on the falling edges of the SSIClk signal.

In the case of a single word transmission, after all bits of the data word have been transferred, the SSIFss line is returned to its idle High state one SSIC1k period after the last bit has been captured.

However, in the case of continuous back-to-back transmissions, the SSIFss signal must be pulsed High between each data word transfer because the slave select pin freezes the data in its serial peripheral register and does not allow it to be altered if the SPH bit is clear. Therefore, the master device must raise the SSIFss pin of the slave device between each data transfer to enable the serial peripheral data write. On completion of the continuous transfer, the SSIFss pin is returned to its idle state one SSIClk period after the last bit has been captured.

15.3.4.4 Freescale SPI Frame Format with SPO=0 and SPH=1

The transfer signal sequence for Freescale SPI format with SPO=0 and SPH=1 is shown in Figure 15-6 on page 966, which covers both single and continuous transfers.

Figure 15-6. Freescale SPI Frame Format with SPO=0 and SPH=1

Note: Q is undefined.

In this configuration, during idle periods:

- SSIC1k is forced Low
- SSIFss is forced High
- The transmit data line SSITx is arbitrarily forced Low
- When the SSI is configured as a master, it enables the SSIClk pad
- When the SSI is configured as a slave, it disables the SSIClk pad

If the SSI is enabled and valid data is in the transmit FIFO, the start of transmission is signified by the SSIFss master signal being driven Low. The master SSITx output is enabled. After an additional one-half SSIC1k period, both master and slave valid data are enabled onto their respective transmission lines. At the same time, the SSIC1k is enabled with a rising edge transition.

Data is then captured on the falling edges and propagated on the rising edges of the SSIC1k signal.

In the case of a single word transfer, after all bits have been transferred, the SSIFss line is returned to its idle High state one SSIClk period after the last bit has been captured.

For continuous back-to-back transfers, the SSIFss pin is held Low between successive data words, and termination is the same as that of the single word transfer.

15.3.4.5 Freescale SPI Frame Format with SPO=1 and SPH=0

Single and continuous transmission signal sequences for Freescale SPI format with SPO=1 and SPH=0 are shown in Figure 15-7 on page 966 and Figure 15-8 on page 967.




Figure 15-7. Freescale SPI Frame Format (Single Transfer) with SPO=1 and SPH=0

Note: Q is undefined.




Figure 15-8. Freescale SPI Frame Format (Continuous Transfer) with SPO=1 and SPH=0

In this configuration, during idle periods:

- SSIClk is forced High
- SSIFss is forced High
- The transmit data line SSITx is arbitrarily forced Low
- When the SSI is configured as a master, it enables the SSIClk pad
- When the SSI is configured as a slave, it disables the SSIClk pad

If the SSI is enabled and valid data is in the transmit FIFO, the start of transmission is signified by the SSIFss master signal being driven Low, causing slave data to be immediately transferred onto the SSIRx line of the master. The master SSITx output pad is enabled.

One-half period later, valid master data is transferred to the SSITx line. Once both the master and slave data have been set, the SSIClk master clock pin becomes Low after one additional half SSIClk period, meaning that data is captured on the falling edges and propagated on the rising edges of the SSIClk signal.

In the case of a single word transmission, after all bits of the data word are transferred, the SSIFss line is returned to its idle High state one SSIClk period after the last bit has been captured.

However, in the case of continuous back-to-back transmissions, the SSIFss signal must be pulsed High between each data word transfer because the slave select pin freezes the data in its serial peripheral register and does not allow it to be altered if the SPH bit is clear. Therefore, the master device must raise the SSIFss pin of the slave device between each data transfer to enable the serial peripheral data write. On completion of the continuous transfer, the SSIFss pin is returned to its idle state one SSIClk period after the last bit has been captured.

15.3.4.6 Freescale SPI Frame Format with SPO=1 and SPH=1

The transfer signal sequence for Freescale SPI format with SPO=1 and SPH=1 is shown in Figure 15-9 on page 968, which covers both single and continuous transfers.

February 20, 2013 967

Figure 15-9. Freescale SPI Frame Format with SPO=1 and SPH=1

Note: Q is undefined.

In this configuration, during idle periods:

- SSIClk is forced High
- SSIFss is forced High
- The transmit data line SSITx is arbitrarily forced Low
- When the SSI is configured as a master, it enables the SSIClk pad
- When the SSI is configured as a slave, it disables the SSIClk pad

If the SSI is enabled and valid data is in the transmit FIFO, the start of transmission is signified by the SSIFss master signal being driven Low. The master SSITx output pad is enabled. After an additional one-half SSIClk period, both master and slave data are enabled onto their respective transmission lines. At the same time, SSIClk is enabled with a falling edge transition. Data is then captured on the rising edges and propagated on the falling edges of the SSIClk signal.

After all bits have been transferred, in the case of a single word transmission, the SSIFss line is returned to its idle high state one SSIClk period after the last bit has been captured.

For continuous back-to-back transmissions, the SSIFss pin remains in its active Low state until the final bit of the last word has been captured and then returns to its idle state as described above.

For continuous back-to-back transfers, the SSIFss pin is held Low between successive data words and termination is the same as that of the single word transfer.

15.3.4.7 MICROWIRE Frame Format

Figure 15-10 on page 968 shows the MICROWIRE frame format for a single frame. Figure 15-11 on page 969 shows the same format when back-to-back frames are transmitted.

SSICIK

SSIFss

SSITx

MSB

N

SSIRx

8-bit control

0 MSB

4 to 16 bits
output data

Figure 15-10. MICROWIRE Frame Format (Single Frame)

968 February 20, 2013
Texas Instruments-Advance Information

MICROWIRE format is very similar to SPI format, except that transmission is half-duplex instead of full-duplex and uses a master-slave message passing technique. Each serial transmission begins with an 8-bit control word that is transmitted from the SSI to the off-chip slave device. During this transmission, no incoming data is received by the SSI. After the message has been sent, the off-chip slave decodes it and, after waiting one serial clock after the last bit of the 8-bit control message has been sent, responds with the required data. The returned data is 4 to 16 bits in length, making the total frame length anywhere from 13 to 25 bits.

In this configuration, during idle periods:

- SSIClk is forced Low
- SSIFss is forced High
- The transmit data line SSITx is arbitrarily forced Low

A transmission is triggered by writing a control byte to the transmit FIFO. The falling edge of SSIFss causes the value contained in the bottom entry of the transmit FIFO to be transferred to the serial shift register of the transmit logic and the MSB of the 8-bit control frame to be shifted out onto the SSITx pin. SSIFss remains Low for the duration of the frame transmission. The SSIRx pin remains tristated during this transmission.

The off-chip serial slave device latches each control bit into its serial shifter on each rising edge of <code>SSIClk</code>. After the last bit is latched by the slave device, the control byte is decoded during a one clock wait-state, and the slave responds by transmitting data back to the SSI. Each bit is driven onto the <code>SSIRx</code> line on the falling edge of <code>SSIClk</code>. The SSI in turn latches each bit on the rising edge of <code>SSIClk</code>. At the end of the frame, for single transfers, the <code>SSIFss</code> signal is pulled High one clock period after the last bit has been latched in the receive serial shifter, causing the data to be transferred to the receive FIFO.

Note: The off-chip slave device can tristate the receive line either on the falling edge of SSIClk after the LSB has been latched by the receive shifter or when the SSIFss pin goes High.

For continuous transfers, data transmission begins and ends in the same manner as a single transfer. However, the SSIFss line is continuously asserted (held Low) and transmission of data occurs back-to-back. The control byte of the next frame follows directly after the LSB of the received data from the current frame. Each of the received values is transferred from the receive shifter on the falling edge of SSIClk, after the LSB of the frame has been latched into the SSI.




Figure 15-11. MICROWIRE Frame Format (Continuous Transfer)

In the MICROWIRE mode, the SSI slave samples the first bit of receive data on the rising edge of SSIClk after SSIFss has gone Low. Masters that drive a free-running SSIClk must ensure that the SSIFss signal has sufficient setup and hold margins with respect to the rising edge of SSIClk.

February 20, 2013 969

Figure 15-12 on page 970 illustrates these setup and hold time requirements. With respect to the SSIClk rising edge on which the first bit of receive data is to be sampled by the SSI slave, SSIFSS must have a setup of at least two times the period of SSIClk on which the SSI operates. With respect to the SSIClk rising edge previous to this edge, SSIFSS must have a hold of at least one SSIClk period.




Figure 15-12. MICROWIRE Frame Format, SSIFss Input Setup and Hold Requirements

15.3.5 DMA Operation

The SSI peripheral provides an interface to the μ DMA controller with separate channels for transmit and receive. The μ DMA operation of the SSI is enabled through the **SSI DMA Control (SSIDMACTL)** register. When μ DMA operation is enabled, the SSI asserts a μ DMA request on the receive or transmit channel when the associated FIFO can transfer data. For the receive channel, a single transfer request is asserted whenever any data is in the receive FIFO. A burst transfer request is asserted whenever the amount of data in the receive FIFO is 4 or more items. For the transmit channel, a single transfer request is asserted whenever at least one empty location is in the transmit FIFO. The burst request is asserted whenever the transmit FIFO has 4 or more empty slots. The single and burst μ DMA transfer requests are handled automatically by the μ DMA controller depending how the μ DMA channel is configured. To enable μ DMA operation for the receive channel, the RXDMAE bit of the **DMA Control (SSIDMACTL)** register should be set. To enable μ DMA operation for the transmit channel, the TXDMAE bit of **SSIDMACTL** should be set. If μ DMA is enabled, then the μ DMA controller triggers an interrupt when a transfer is complete. The interrupt occurs on the SSI interrupt vector. Therefore, if interrupts are used for SSI operation and μ DMA is enabled, the SSI interrupt handler must be designed to handle the μ DMA completion interrupt.

See "Micro Direct Memory Access (μ DMA)" on page 582 for more details about programming the μ DMA controller.

15.4 Initialization and Configuration

To enable and initialize the SSI, the following steps are necessary:

- 1. Enable the SSI module using the RCGCSSI register (see page 337).
- **2.** Enable the clock to the appropriate GPIO module via the **RCGCGPIO** register (see page 330). To find out which GPIO port to enable, refer to Table 23-5 on page 1367.
- 3. Set the GPIO AFSEL bits for the appropriate pins (see page 670). To determine which GPIOs to configure, see Table 23-4 on page 1358.

4. Configure the PMCn fields in the **GPIOPCTL** register to assign the SSI signals to the appropriate pins. See page 688 and Table 23-5 on page 1367.

For each of the frame formats, the SSI is configured using the following steps:

- 1. Ensure that the SSE bit in the SSICR1 register is clear before making any configuration changes.
- 2. Select whether the SSI is a master or slave:
 - **a.** For master operations, set the **SSICR1** register to 0x0000.0000.
 - **b.** For slave mode (output enabled), set the **SSICR1** register to 0x0000.0004.
 - c. For slave mode (output disabled), set the **SSICR1** register to 0x0000.000C.
- 3. Configure the SSI clock source by writing to the SSICC register.
- **4.** Configure the clock prescale divisor by writing the **SSICPSR** register.
- 5. Write the **SSICR0** register with the following configuration:
 - Serial clock rate (SCR)
 - Desired clock phase/polarity, if using Freescale SPI mode (SPH and SPO)
 - The protocol mode: Freescale SPI, TI SSF, MICROWIRE (FRF)
 - The data size (DSS)
- **6.** Optionally, configure the μDMA channel (see "Micro Direct Memory Access (μDMA)" on page 582) and enable the DMA option(s) in the **SSIDMACTL** register.
- 7. Enable the SSI by setting the SSE bit in the SSICR1 register.

As an example, assume the SSI must be configured to operate with the following parameters:

- Master operation
- Freescale SPI mode (SPO=1, SPH=1)
- 1 Mbps bit rate
- 8 data bits

Assuming the system clock is 20 MHz, the bit rate calculation would be:

```
SSIClk = SysClk / (CPSDVSR * (1 + SCR))
1x10<sup>6</sup> = 20x10<sup>6</sup> / (CPSDVSR * (1 + SCR))
```

In this case, if CPSDVSR=0x2, SCR must be 0x9.

The configuration sequence would be as follows:

- 1. Ensure that the SSE bit in the SSICR1 register is clear.
- 2. Write the **SSICR1** register with a value of 0x0000.0000.

- 3. Write the **SSICPSR** register with a value of 0x0000.0002.
- 4. Write the **SSICR0** register with a value of 0x0000.09C7.
- 5. The SSI is then enabled by setting the SSE bit in the SSICR1 register.

15.5 Register Map

Table 15-2 on page 972 lists the SSI registers. The offset listed is a hexadecimal increment to the register's address, relative to that SSI module's base address:

SSI0: 0x4000.8000SSI1: 0x4000.9000SSI2: 0x4000.A000SSI3: 0x4000.B000

Note that the SSI module clock must be enabled before the registers can be programmed (see page 337). There must be a delay of 3 system clocks after the SSI module clock is enabled before any SSI module registers are accessed.

Note: The SSI must be disabled (see the SSE bit in the **SSICR1** register) before any of the control registers are reprogrammed.

Table 15-2. SSI Register Map

Offset	Name	Туре	Reset	Description	See page
0x000	SSICR0	R/W	0x0000.0000	SSI Control 0	974
0x004	SSICR1	R/W	0x0000.0000	SSI Control 1	976
0x008	SSIDR	R/W	0x0000.0000	SSI Data	978
0x00C	SSISR	RO	0x0000.0003	SSI Status	979
0x010	SSICPSR	R/W	0x0000.0000	SSI Clock Prescale	981
0x014	SSIIM	R/W	0x0000.0000	SSI Interrupt Mask	982
0x018	SSIRIS	RO	0x0000.0008	SSI Raw Interrupt Status	983
0x01C	SSIMIS	RO	0x0000.0000	SSI Masked Interrupt Status	985
0x020	SSIICR	W1C	0x0000.0000	SSI Interrupt Clear	987
0x024	SSIDMACTL	R/W	0x0000.0000	SSI DMA Control	988
0xFC8	SSICC	R/W	0x0000.0000	SSI Clock Configuration	989
0xFD0	SSIPeriphID4	RO	0x0000.0000	SSI Peripheral Identification 4	990
0xFD4	SSIPeriphID5	RO	0x0000.0000	SSI Peripheral Identification 5	991
0xFD8	SSIPeriphID6	RO	0x0000.0000	SSI Peripheral Identification 6	992
0xFDC	SSIPeriphID7	RO	0x0000.0000	SSI Peripheral Identification 7	993
0xFE0	SSIPeriphID0	RO	0x0000.0022	SSI Peripheral Identification 0	994
0xFE4	SSIPeriphID1	RO	0x0000.0000	SSI Peripheral Identification 1	995
0xFE8	SSIPeriphID2	RO	0x0000.0018	SSI Peripheral Identification 2	996

Table 15-2. SSI Register Map (continued)

Offset	Name	Type	Reset	Description	See page
0xFEC	SSIPeriphID3	RO	0x0000.0001	SSI Peripheral Identification 3	997
0xFF0	SSIPCellID0	RO	0x0000.000D	SSI PrimeCell Identification 0	998
0xFF4	SSIPCellID1	RO	0x0000.00F0	SSI PrimeCell Identification 1	999
0xFF8	SSIPCellID2	RO	0x0000.0005	SSI PrimeCell Identification 2	1000
0xFFC	SSIPCellID3	RO	0x0000.00B1	SSI PrimeCell Identification 3	1001

15.6 Register Descriptions

The remainder of this section lists and describes the SSI registers, in numerical order by address offset.

Register 1: SSI Control 0 (SSICR0), offset 0x000


The **SSICR0** register contains bit fields that control various functions within the SSI module. Functionality such as protocol mode, clock rate, and data size are configured in this register.

SSI Control 0 (SSICR0)

SSI0 base: 0x4000.8000 SSI1 base: 0x4000.9000 SSI2 base: 0x4000.A000 SSI3 base: 0x4000.B000

Offset 0x000

Type R/W, reset 0x0000.0000



Bit/Field	Name	Type	Reset	Description
31:16	reserved	RO	0x0000	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
15:8	SCR	R/W	0x00	SSI Serial Clock Rate
				This bit field is used to generate the transmit and receive bit rate of the SSI. The bit rate is:
				BR=SysClk/(CPSDVSR * (1 + SCR))
				where CPSDVSR is an even value from 2-254 programmed in the SSICPSR register, and SCR is a value from 0-255.
7	SPH	R/W	0	SSI Serial Clock Phase
				This bit is only applicable to the Freescale SPI Format.
				The SPH control bit selects the clock edge that captures data and allows it to change state. This bit has the most impact on the first bit transmitted by either allowing or not allowing a clock transition before the first data capture edge.
				Value Description
				0 Data is captured on the first clock edge transition.
				1 Data is captured on the second clock edge transition.
6	SPO	R/W	0	SSI Serial Clock Polarity
				VI D : 6

Value Description

- 0 A steady state Low value is placed on the SSIC1k pin.
- 1 A steady state High value is placed on the SSIClk pin when data is not being transferred.

Bit/Field	Name	Туре	Reset	Description
5:4	FRF	R/W	0x0	SSI Frame Format Select
				Value Frame Format 0x0 Freescale SPI Frame Format 0x1 Texas Instruments Synchronous Serial Frame Format 0x2 MICROWIRE Frame Format 0x3 Reserved
3:0	DSS	R/W	0x0	SSI Data Size Select
				Value Data Size
				0x0-0x2 Reserved
				0x3 4-bit data
				0x4 5-bit data
				0x5 6-bit data
				0x6 7-bit data
				0x7 8-bit data
				0x8 9-bit data
				0x9 10-bit data
				0xA 11-bit data
				0xB 12-bit data
				0xC 13-bit data
				0xD 14-bit data
				0xE 15-bit data
				0xF 16-bit data

Register 2: SSI Control 1 (SSICR1), offset 0x004

The **SSICR1** register contains bit fields that control various functions within the SSI module. Master and slave mode functionality is controlled by this register.

SSI Control 1 (SSICR1)

SSI0 base: 0x4000.8000 SSI1 base: 0x4000.9000 SSI2 base: 0x4000.A000 SSI3 base: 0x4000.B000

Offset 0x004

Bit/Field

31:6

4

Name

reserved

EOT

Type

RO


R/W

Reset

0.0000.0

0

Type R/W, reset 0x0000.0000



				compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
5	SLBY6	R/W	0	Slave Bypass Mode
				Value Description
				O SSI Module operates standard mode such that the slave is clocked at a 12:1 ratio of system clock to SSInCLK.
				1 SSI module functions such that the slave operates at a 6:1 ratio of system clock to SSInCLK.

Description

End of Transmission

This bit is only valid for Master mode devices and operations (MS = 0x0).

Software should not rely on the value of a reserved bit. To provide

Value Description

- The TXRIS interrupt indicates that the transmit FIFO is half full or less.
- 1 The End of Transmit interrupt mode for the TXRIS interrupt is enabled.

Note:

In Freescale SPI mode only, a condition can be created where an EOT interrupt is generated for every byte transferred even if the FIFO is full. If the EOT bit has been set to 0 in an integrated slave SSI and the μDMA has been configured to transfer data from this SSI to a Master SSI on the device using external loopback, an EOT interrupt is generated by the SSI slave for every byte even if the FIFO is full.

Bit/Field	Name	Туре	Reset	Description
3	SOD	R/W	0	SSI Slave Mode Output Disable This bit is relevant only in the Slave mode (MS=1). In multiple-slave systems, it is possible for the SSI master to broadcast a message to all slaves in the system while ensuring that only one slave drives data onto the serial output line. In such systems, the TXD lines from multiple slaves could be tied together. To operate in such a system, the SOD bit can be configured so that the SSI slave does not drive the SSITX pin.
				Value Description
				0 SSI can drive the SSITx output in Slave mode.
				1 SSI must not drive the SSITx output in Slave mode.
2	MS	R/W	0	SSI Master/Slave Select
				This bit selects Master or Slave mode and can be modified only when the SSI is disabled (SSE=0).
				Value Description
				0 The SSI is configured as a master.
				1 The SSI is configured as a slave.
1	SSE	R/W	0	SSI Synchronous Serial Port Enable
				Value Description
				0 SSI operation is disabled.
				1 SSI operation is enabled.
				Note: This bit must be cleared before any control registers are reprogrammed.
0	LBM	R/W	0	SSI Loopback Mode
				Value Description
				0 Normal serial port operation enabled.
				Output of the transmit serial shift register is connected internally to the input of the receive serial shift register.

February 20, 2013 977

Register 3: SSI Data (SSIDR), offset 0x008

Important: This register is read-sensitive. See the register description for details.

The **SSIDR** register is 16-bits wide. When the **SSIDR** register is read, the entry in the receive FIFO that is pointed to by the current FIFO read pointer is accessed. When a data value is removed by the SSI receive logic from the incoming data frame, it is placed into the entry in the receive FIFO pointed to by the current FIFO write pointer.

When the **SSIDR** register is written to, the entry in the transmit FIFO that is pointed to by the write pointer is written to. Data values are removed from the transmit FIFO one value at a time by the transmit logic. Each data value is loaded into the transmit serial shifter, then serially shifted out onto the SSITX pin at the programmed bit rate.

When a data size of less than 16 bits is selected, the user must right-justify data written to the transmit FIFO. The transmit logic ignores the unused bits. Received data less than 16 bits is automatically right-justified in the receive buffer.


When the SSI is programmed for MICROWIRE frame format, the default size for transmit data is eight bits (the most significant byte is ignored). The receive data size is controlled by the programmer. The transmit FIFO and the receive FIFO are not cleared even when the SSE bit in the **SSICR1** register is cleared, allowing the software to fill the transmit FIFO before enabling the SSI.

SSI Data (SSIDR)

SSI0 base: 0x4000.8000 SSI1 base: 0x4000.9000 SSI2 base: 0x4000.A000 SSI3 base: 0x4000.B000

Offset 0x008

Type R/W, reset 0x0000.0000



Bit/Field	Name	Type	Reset	Description
31:16	reserved	RO	0x0000	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
15:0	DATA	R/W	0x0000	SSI Receive/Transmit Data

A read operation reads the receive FIFO. A write operation writes the transmit FIFO.

Software must right-justify data when the SSI is programmed for a data size that is less than 16 bits. Unused bits at the top are ignored by the transmit logic. The receive logic automatically right-justifies the data.

Register 4: SSI Status (SSISR), offset 0x00C


The **SSISR** register contains bits that indicate the FIFO fill status and the SSI busy status.

SSI Status (SSISR)

SSI0 base: 0x4000.8000 SSI1 base: 0x4000.9000 SSI2 base: 0x4000.A000 SSI3 base: 0x4000.B000

Offset 0x00C

Type RO, reset 0x0000.0003



Bit/Field	Name	Туре	Reset	Description
31:5	reserved	RO	0x0000.00	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
4	BSY	RO	0	SSI Busy Bit
				Value Description
				0 The SSI is idle.
				1 The SSI is currently transmitting and/or receiving a frame, or the transmit FIFO is not empty.
3	RFF	RO	0	SSI Receive FIFO Full
				Value Description
				0 The receive FIFO is not full.
				1 The receive FIFO is full.
2	RNE	RO	0	SSI Receive FIFO Not Empty
				Value Description
				0 The receive FIFO is empty.
				1 The receive FIFO is not empty.
1	TNF	RO	1	SSI Transmit FIFO Not Full
				Value Description
				0 The transmit FIFO is full.
				1 The transmit FIFO is not full.

Bit/Field	Name	Type	Reset	Description
0	TFE	RO	1	SSI Transmit FIFO Empty
				Value Description
				0 The transmit FIFO is not empty.
				1 The transmit FIFO is empty.

Register 5: SSI Clock Prescale (SSICPSR), offset 0x010

The **SSICPSR** register specifies the division factor which is used to derive the SSIC1k from the system clock. The clock is further divided by a value from 1 to 256, which is 1 + SCR. SCR is programmed in the **SSICR0** register. The frequency of the SSIC1k is defined by:

```
SSIClk = SysClk / (CPSDVSR * (1 + SCR))
```


The value programmed into this register must be an even number between 2 and 254. The least-significant bit of the programmed number is hard-coded to zero. If an odd number is written to this register, data read back from this register has the least-significant bit as zero.

SSI Clock Prescale (SSICPSR)

SSI0 base: 0x4000.8000 SSI1 base: 0x4000.9000 SSI2 base: 0x4000.A000 SSI3 base: 0x4000.B000

Offset 0x010

Type R/W, reset 0x0000.0000



Bit/Field	Name	Type	Reset	Description
31:8	reserved	RO	0x00	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
7:0	CPSDVSR	R/W	0x00	SSI Clock Prescale Divisor

This value must be an even number from 2 to 254, depending on the frequency of ${\tt SSIClk}.$ The LSB always returns 0 on reads.

Register 6: SSI Interrupt Mask (SSIIM), offset 0x014

The **SSIIM** register is the interrupt mask set or clear register. It is a read/write register and all bits are cleared on reset.

On a read, this register gives the current value of the mask on the corresponding interrupt. Setting a bit sets the mask, preventing the interrupt from being signaled to the interrupt controller. Clearing a bit clears the corresponding mask, enabling the interrupt to be sent to the interrupt controller.


SSI Interrupt Mask (SSIIM)

SSI0 base: 0x4000.8000 SSI1 base: 0x4000.9000 SSI2 base: 0x4000.A000

SSI3 base: 0x4000.B000

Offset 0x014

Type R/W, reset 0x0000.0000



Bit/Field	Name	Type	Reset	Description
31:4	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
3	TXIM	R/W	0	SSI Transmit FIFO Interrupt Mask
				Value Description
				0 The transmit FIFO interrupt is masked.
				1 The transmit FIFO interrupt is not masked.
2	RXIM	R/W	0	SSI Receive FIFO Interrupt Mask
				Value Description
				0 The receive FIFO interrupt is masked.
				1 The receive FIFO interrupt is not masked.
1	RTIM	R/W	0	SSI Receive Time-Out Interrupt Mask
				Value Description
				The receive FIFO time-out interrupt is masked.
				1 The receive FIFO time-out interrupt is not masked.
0	RORIM	R/W	0	SSI Receive Overrun Interrupt Mask
				Value Description
				0 The receive FIFO overrun interrupt is masked.
				1 The receive FIFO overrun interrupt is not masked.

Register 7: SSI Raw Interrupt Status (SSIRIS), offset 0x018


The **SSIRIS** register is the raw interrupt status register. On a read, this register gives the current raw status value of the corresponding interrupt prior to masking. A write has no effect.

SSI Raw Interrupt Status (SSIRIS)

SSI0 base: 0x4000.8000 SSI1 base: 0x4000.9000 SSI2 base: 0x4000.A000 SSI3 base: 0x4000.B000

Offset 0x018

Type RO, reset 0x0000.0008



Bit/Field	Name	Туре	Reset	Description
31:4	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
3	TXRIS	RO	1	SSI Transmit FIFO Raw Interrupt Status
				 Value Description No interrupt. If the EOT bit in the SSICR1 register is clear, the transmit FIFO is half empty or less. If the EOT bit is set, the transmit FIFO is empty, and the last bit has been transmitted out of the serializer. This bit is cleared when the transmit FIFO is more than half full (if the EOT bit is clear) or when it has any data in it (if the EOT bit is set).
2	RXRIS	RO	0	SSI Receive FIFO Raw Interrupt Status Value Description 0 No interrupt. 1 The receive FIFO is half full or more. This bit is cleared when the receive FIFO is less than half full.
1	RTRIS	RO	0	SSI Receive Time-Out Raw Interrupt Status

Value Description

0 No interrupt.

1 The receive time-out has occurred.

This bit is cleared when a 1 is written to the RTIC bit in the SSI Interrupt Clear (SSIICR) register.

Bit/Field	Name	Туре	Reset	Description
0	RORRIS	RO	0	SSI Receive Overrun Raw Interrupt Status
				Value Description
				0 No interrupt.
				1 The receive FIFO has overflowed
				This bit is cleared when a 1 is written to the RORIC bit in the SSI Interrupt Clear (SSIICR) register.


Register 8: SSI Masked Interrupt Status (SSIMIS), offset 0x01C

The **SSIMIS** register is the masked interrupt status register. On a read, this register gives the current masked status value of the corresponding interrupt. A write has no effect.

SSI Masked Interrupt Status (SSIMIS)

SSI0 base: 0x4000.8000 SSI1 base: 0x4000.9000 SSI2 base: 0x4000.A000 SSI3 base: 0x4000.B000 Offset 0x01C

Type RO, reset 0x0000.0000



0 0	0	0	0	0	0	0	0	0	0	0	0	0	0
Naı	me	Ту	ре	Reset	Desc	cription							
rese	rved	R	0	0	comp	patibility	with futu	ıre prodi	ucts, the	value of	a reserv	•	
TXN	ИIS	R	0	0	SSI	Transmi	t FIFO M	lasked lı	nterrupt	Status			
					Valu	ie Desc	ription						
					0	An in	terrupt h	as not o	ccurred	or is ma	sked.		
					1	being	g half em	pty or le	ss (if the	EOT bit	is clear)	or due t	
RXI	MIS	R	0	0	SSI	Receive	FIFO M	asked In	terrupt S	Status			
					Valu	ie Desc	ription						
					0	An in	terrupt h	as not o	ccurred	or is ma	sked.		
					1					gnaled d	ue to the	e receive	FIFO
					This	bit is cle	eared wh	en the r	eceive F	IFO is le	ss than I	half full.	
RTM	MIS	R	0	0	SSI	Receive	Time-O	ut Maske	ed Interru	upt Statu	ıs		
	Nai resei TXN	Name reserved TXMIS RXMIS	Name Ty reserved R TXMIS R RXMIS R	Name Type reserved RO TXMIS RO	Name Type Reset reserved RO 0 TXMIS RO 0 RXMIS RO 0	Name Type Reset Description of the reserved RO 0 Software preserved TXMIS RO 0 SSI Value 0 1 This the EXMIS RO 0 SSI Value 0 1 This the EXMIS RO 0 THIS RO THIS ROUND RO	Name Type Reset Description reserved RO 0 Software sho compatibility preserved at TXMIS RO 0 SSI Transmi Value Description 1 An under the EOT bit is RXMIS RO 0 SSI Receive Value Description 0 An in 1 An under the EOT bit is clearly being trans This bit is clearly being This bit is clearly being trans This bit is clearly being This bit is clearly being trans This bit is clearly being This bit is clearly being trans This bit is clearly being This bit is clearly being trans This bit is clearly being transpired to the property of the prope	Name Type Reset Description reserved RO 0 Software should not compatibility with futty preserved across a not start the preserved across and the preserved across acro	Name Type Reset Description reserved RO 0 Software should not rely on the compatibility with future product preserved across a read-mode preserved across a read	Name Type Reset Description reserved RO 0 Software should not rely on the value compatibility with future products, the preserved across a read-modify-write TXMIS RO 0 SSI Transmit FIFO Masked Interrupt Value Description 0 An interrupt has not occurred 1 An unmasked interrupt was si being half empty or less (if the transmission of the last data but the EOT bit is clear) or when it has an RXMIS RO 0 SSI Receive FIFO Masked Interrupt SValue Description 0 An interrupt has not occurred 1 An unmasked interrupt was si being half full or more. This bit is cleared when the receive FIFO Masked Interrupt was si being half full or more.	Name Type Reset Description reserved RO 0 Software should not rely on the value of a rescompatibility with future products, the value of preserved across a read-modify-write operation TXMIS RO 0 SSI Transmit FIFO Masked Interrupt Status Value Description 0 An interrupt has not occurred or is made to being half empty or less (if the EOT bit transmission of the last data bit (if the This bit is cleared when the transmit FIFO is not the EOT bit is clear) or when it has any data in the EOT bit is clear) or when it has any data in the EOT bit is clear or when it has a read model.	Name Type Reset Description reserved RO 0 Software should not rely on the value of a reserved bit compatibility with future products, the value of a reserved across a read-modify-write operation. TXMIS RO 0 SSI Transmit FIFO Masked Interrupt Status Value Description 0 An interrupt has not occurred or is masked. 1 An unmasked interrupt was signaled due to the being half empty or less (if the EOT bit is clear) transmission of the last data bit (if the EOT bit is clear) or when it has any data in it (if the EOT bit is clear) or when it has any data in it (if the RXMIS RO 0 SSI Receive FIFO Masked Interrupt Status Value Description 0 An interrupt has not occurred or is masked. 1 An unmasked interrupt was signaled due to the being half full or more. This bit is cleared when the receive FIFO is less than it	Name Type Reset Description reserved RO 0 Software should not rely on the value of a reserved bit. To provocompatibility with future products, the value of a reserved bit structure products, the value of a reserved bit st

Value Description

- 0 An interrupt has not occurred or is masked.
- 1 An unmasked interrupt was signaled due to the receive time

This bit is cleared when a 1 is written to the RTIC bit in the SSI Interrupt Clear (SSIICR) register.

Bit/Field	Name	Туре	Reset	Description
0	RORMIS	RO	0	SSI Receive Overrun Masked Interrupt Status
				Value Description
				0 An interrupt has not occurred or is masked.
				An unmasked interrupt was signaled due to the receive FIFO overflowing.
				This bit is cleared when a 1 is written to the RORIC bit in the SSI Interrupt Clear (SSIICR) register.

Register 9: SSI Interrupt Clear (SSIICR), offset 0x020


The **SSIICR** register is the interrupt clear register. On a write of 1, the corresponding interrupt is cleared. A write of 0 has no effect.

SSI Interrupt Clear (SSIICR)

SSI0 base: 0x4000.8000 SSI1 base: 0x4000.9000 SSI2 base: 0x4000.A000 SSI3 base: 0x4000.B000

Offset 0x020

Type W1C, reset 0x0000.0000



Bit/Field	Name	Туре	Reset	Description
31:2	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
1	RTIC	W1C	0	SSI Receive Time-Out Interrupt Clear
				Writing a 1 to this bit clears the RTRIS bit in the SSIRIS register and the RTMIS bit in the SSIMIS register.
0	RORIC	W1C	0	SSI Receive Overrun Interrupt Clear
				Writing a 1 to this bit clears the RORRIS bit in the SSIRIS register and the RORMIS bit in the SSIMIS register.

Register 10: SSI DMA Control (SSIDMACTL), offset 0x024


The **SSIDMACTL** register is the μ DMA control register.

SSI DMA Control (SSIDMACTL)

SSI0 base: 0x4000.8000 SSI1 base: 0x4000.9000 SSI2 base: 0x4000.A000 SSI3 base: 0x4000.B000

Offset 0x024

Type R/W, reset 0x0000.0000



Bit/Field	Name	Type	Reset	Description
31:2	reserved	RO	0x0000.000	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
1	TXDMAE	R/W	0	Transmit DMA Enable
				Value Description
				0 μDMA for the transmit FIFO is disabled.
				1 μ DMA for the transmit FIFO is enabled.
0	RXDMAE	R/W	0	Receive DMA Enable

Value Description

- 0 μ DMA for the receive FIFO is disabled.
- 1 μDMA for the receive FIFO is enabled.

Register 11: SSI Clock Configuration (SSICC), offset 0xFC8

The SSICC register controls the baud clock source for the SSI module.


Note: If the PIOSC is used for the SSI baud clock, the system clock frequency must be at least 16 MHz in Run mode.

SSI Clock Configuration (SSICC)

SSI0 base: 0x4000.8000 SSI1 base: 0x4000.9000 SSI2 base: 0x4000.A000 SSI3 base: 0x4000.B000

Offset 0xFC8

Type R/W, reset 0x0000.0000



Bit/Field	Name	Type	Reset	Description
31:4	reserved	RO	0x0000.000	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
3:0	CS	R/W	0	SSI Baud Clock Source

0x6 - 0xF Reserved

The following table specifies the source that generates for the SSI baud clock:

Value Description

0x0 System clock (based on clock source and divisor factor)

0x1-0x4 reserved

0x5 PIOSC


Register 12: SSI Peripheral Identification 4 (SSIPeriphID4), offset 0xFD0

The SSIPeriphIDn registers are hard-coded and the fields within the register determine the reset value.

SSI Peripheral Identification 4 (SSIPeriphID4)

SSI0 base: 0x4000.8000 SSI1 base: 0x4000.9000 SSI2 base: 0x4000.A000 SSI3 base: 0x4000.B000 Offset 0xFD0

Type RO, reset 0x0000.0000



Bit/Field	Name	Type	Reset	Description
31:8	reserved	RO	0x0000.00	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
7:0	PID4	RO	0x00	SSI Peripheral ID Register [7:0]


Register 13: SSI Peripheral Identification 5 (SSIPeriphID5), offset 0xFD4

The SSIPeriphIDn registers are hard-coded and the fields within the register determine the reset value.

SSI Peripheral Identification 5 (SSIPeriphID5)

SSI0 base: 0x4000.8000 SSI1 base: 0x4000.9000 SSI2 base: 0x4000.A000 SSI3 base: 0x4000.B000 Offset 0xFD4

Type RO, reset 0x0000.0000



Bit/Field	Name	Type	Reset	Description
31:8	reserved	RO	0x0000.00	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
7:0	PID5	RO	0x00	SSI Peripheral ID Register [15:8]


Register 14: SSI Peripheral Identification 6 (SSIPeriphID6), offset 0xFD8

The SSIPeriphIDn registers are hard-coded and the fields within the register determine the reset value.

SSI Peripheral Identification 6 (SSIPeriphID6)

SSI0 base: 0x4000.8000 SSI1 base: 0x4000.9000 SSI2 base: 0x4000.A000 SSI3 base: 0x4000.B000 Offset 0xFD8

Type RO, reset 0x0000.0000



Bit/Field	Name	Type	Reset	Description
31:8	reserved	RO	0x0000.00	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
7:0	PID6	RO	0x00	SSI Peripheral ID Register [23:16]


Register 15: SSI Peripheral Identification 7 (SSIPeriphID7), offset 0xFDC

The SSIPeriphIDn registers are hard-coded and the fields within the register determine the reset value.

SSI Peripheral Identification 7 (SSIPeriphID7)

SSI0 base: 0x4000.8000 SSI1 base: 0x4000.9000 SSI2 base: 0x4000.A000 SSI3 base: 0x4000.B000 Offset 0xFDC

Type RO, reset 0x0000.0000



Bit/Field	Name	Type	Reset	Description
31:8	reserved	RO	0x0000.00	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
7:0	PID7	RO	0x00	SSI Peripheral ID Register [31:24]


Register 16: SSI Peripheral Identification 0 (SSIPeriphID0), offset 0xFE0

The SSIPeriphIDn registers are hard-coded and the fields within the register determine the reset value.

SSI Peripheral Identification 0 (SSIPeriphID0)

SSI0 base: 0x4000.8000 SSI1 base: 0x4000.9000 SSI2 base: 0x4000.A000 SSI3 base: 0x4000.B000 Offset 0xFE0

Type RO, reset 0x0000.0022



Bit/Field	Name	Type	Reset	Description
31:8	reserved	RO	0x0000.00	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
7:0	PID0	RO	0x22	SSI Peripheral ID Register [7:0]


Register 17: SSI Peripheral Identification 1 (SSIPeriphID1), offset 0xFE4

The SSIPeriphIDn registers are hard-coded and the fields within the register determine the reset value.

SSI Peripheral Identification 1 (SSIPeriphID1)

SSI0 base: 0x4000.8000 SSI1 base: 0x4000.9000 SSI2 base: 0x4000.A000 SSI3 base: 0x4000.B000 Offset 0xFE4

Type RO, reset 0x0000.0000



Bit/Field	Name	Type	Reset	Description
31:8	reserved	RO	0x0000.00	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
7:0	PID1	RO	0x00	SSI Peripheral ID Register [15:8]


Register 18: SSI Peripheral Identification 2 (SSIPeriphID2), offset 0xFE8

The SSIPeriphIDn registers are hard-coded and the fields within the register determine the reset value.

SSI Peripheral Identification 2 (SSIPeriphID2)

SSI0 base: 0x4000.8000 SSI1 base: 0x4000.9000 SSI2 base: 0x4000.A000 SSI3 base: 0x4000.B000 Offset 0xFE8

Type RO, reset 0x0000.0018



Bit/Field	Name	Type	Reset	Description
31:8	reserved	RO	0x0000.00	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
7:0	PID2	RO	0x18	SSI Peripheral ID Register [23:16]

Register 19: SSI Peripheral Identification 3 (SSIPeriphID3), offset 0xFEC


The SSIPeriphIDn registers are hard-coded and the fields within the register determine the reset value.

SSI Peripheral Identification 3 (SSIPeriphID3)

SSI0 base: 0x4000.8000 SSI1 base: 0x4000.9000 SSI2 base: 0x4000.A000 SSI3 base: 0x4000.B000

Offset 0xFEC

Type RO, reset 0x0000.0001



Bit/Field	Name	Type	Reset	Description
31:8	reserved	RO	0x0000.00	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
7:0	PID3	RO	0x01	SSI Peripheral ID Register [31:24]


Register 20: SSI PrimeCell Identification 0 (SSIPCellID0), offset 0xFF0

The SSIPCeIIIDn registers are hard-coded, and the fields within the register determine the reset value.

SSI PrimeCell Identification 0 (SSIPCellID0)

SSI0 base: 0x4000.8000 SSI1 base: 0x4000.9000 SSI2 base: 0x4000.A000 SSI3 base: 0x4000.B000 Offset 0xFF0

Type RO, reset 0x0000.000D



Bit/Field	Name	Type	Reset	Description
31:8	reserved	RO	0x0000.00	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
7:0	CID0	RO	0x0D	SSI PrimeCell ID Register [7:0]

Register 21: SSI PrimeCell Identification 1 (SSIPCellID1), offset 0xFF4


The **SSIPCeIIIDn** registers are hard-coded, and the fields within the register determine the reset value.

SSI PrimeCell Identification 1 (SSIPCellID1)

SSI0 base: 0x4000.8000 SSI1 base: 0x4000.9000 SSI2 base: 0x4000.A000 SSI3 base: 0x4000.B000

Offset 0xFF4

Type RO, reset 0x0000.00F0



Bit/Field	Name	Type	Reset	Description
31:8	reserved	RO	0x0000.00	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
7:0	CID1	RO	0xF0	SSI PrimeCell ID Register [15:8]


Register 22: SSI PrimeCell Identification 2 (SSIPCellID2), offset 0xFF8

The SSIPCeIIIDn registers are hard-coded, and the fields within the register determine the reset value.

SSI PrimeCell Identification 2 (SSIPCelIID2)

SSI0 base: 0x4000.8000 SSI1 base: 0x4000.9000 SSI2 base: 0x4000.A000 SSI3 base: 0x4000.B000 Offset 0xFF8

Type RO, reset 0x0000.0005



Bit/Field	Name	Type	Reset	Description
31:8	reserved	RO	0x0000.00	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
7:0	CID2	RO	0x05	SSI PrimeCell ID Register [23:16]


Register 23: SSI PrimeCell Identification 3 (SSIPCelIID3), offset 0xFFC

The SSIPCeIIIDn registers are hard-coded, and the fields within the register determine the reset value.

SSI PrimeCell Identification 3 (SSIPCellID3)

SSI0 base: 0x4000.8000 SSI1 base: 0x4000.9000 SSI2 base: 0x4000.A000 SSI3 base: 0x4000.B000 Offset 0xFFC

Type RO, reset 0x0000.00B1



Bit/Field	Name	Type	Reset	Description
31:8	reserved	RO	0x0000.00	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
7:0	CID3	RO	0xB1	SSI PrimeCell ID Register [31:24]

16 Inter-Integrated Circuit (I²C) Interface


The Inter-Integrated Circuit (I²C) bus provides bi-directional data transfer through a two-wire design (a serial data line SDA and a serial clock line SCL), and interfaces to external I²C devices such as serial memory (RAMs and ROMs), networking devices, LCDs, tone generators, and so on. The I²C bus may also be used for system testing and diagnostic purposes in product development and manufacturing. The LM4F232H5QC microcontroller includes providing the ability to communicate (both transmit and receive) with other I²C devices on the bus.

The Stellaris[®] LM4F232H5QC controller includes I²C modules with the following features:

- Devices on the I²C bus can be designated as either a master or a slave
 - Supports both transmitting and receiving data as either a master or a slave
 - Supports simultaneous master and slave operation
- Four I²C modes
 - Master transmit
 - Master receive
 - Slave transmit
 - Slave receive
- Four transmission speeds:
 - Standard (100 Kbps)
 - Fast-mode (400 Kbps)
 - Fast-mode plus (1 Mbps)
 - High-speed mode (3.33 Mbps)
- Clock low timeout interrupt
- Dual slave address capability
- Glitch suppression
- Master and slave interrupt generation
 - Master generates interrupts when a transmit or receive operation completes (or aborts due to an error)
 - Slave generates interrupts when data has been transferred or requested by a master or when a START or STOP condition is detected
- Master with arbitration and clock synchronization, multimaster support, and 7-bit addressing mode

16.1 Block Diagram

Figure 16-1. I²C Block Diagram



16.2 Signal Description

The following table lists the external signals of the I^2C interface and describes the function of each. The I^2C interface signals are alternate functions for some GPIO signals and default to be GPIO signals at reset, with the exception of the I^2COSCL and I^2CSDA pins which default to the I^2C function. The column in the table below titled "Pin Mux/Pin Assignment" lists the possible GPIO pin placements for the I^2C signals. The AFSEL bit in the **GPIO Alternate Function Select (GPIOAFSEL)** register (page 670) should be set to choose the I^2C function. The number in parentheses is the encoding that must be programmed into the PMCn field in the **GPIO Port Control (GPIOPCTL)** register (page 688) to assign the I^2C signal to the specified GPIO port pin. Note that the I^2CSDA pin should be set to open drain using the **GPIO Open Drain Select (GPIOODR)** register. For more information on configuring GPIOs, see "General-Purpose Input/Outputs (GPIOs)" on page 646.

Table 16-1. I2C Signals (100LQFP)

Pin Name	Pin Number	Pin Mux / Pin Assignment	Pin Type	Buffer Type ^a	Description
I2C0SCL	72	PB2 (3)	I/O	OD	I ² C module 0 clock. Note that this signal has an active pull-up. The corresponding port pin should not be configured as open drain.
I2C0SDA	73	PB3 (3)	I/O	OD	I ² C module 0 data.
I2C1SCL	34 74	PA6 (3) PG4 (3)	I/O	OD	I ² C module 1 clock. Note that this signal has an active pull-up. The corresponding port pin should not be configured as open drain.
I2C1SDA	35 75	PA7 (3) PG5 (3)	I/O	OD	I ² C module 1 data.
I2C2SCL	36 95	PF6 (3) PE4 (3)	I/O	OD	I ² C module 2 clock. Note that this signal has an active pull-up. The corresponding port pin should not be configured as open drain.
I2C2SDA	58 96	PF7 (3) PE5 (3)	I/O	OD	I ² C module 2 data.
I2C3SCL	1 62	PD0 (3) PG0 (3)	I/O	OD	I ² C module 3 clock. Note that this signal has an active pull-up. The corresponding port pin should not be configured as open drain.

Pin Name	Pin Number	Pin Mux / Pin Assignment	Pin Type	Buffer Type ^a	Description
I2C3SDA	2 61	PD1 (3) PG1 (3)	I/O	OD	I ² C module 3 data.
I2C4SCL	60	PG2 (3)	I/O	OD	I ² C module 4 clock. Note that this signal has an active pull-up. The corresponding port pin should not be configured as open drain.
I2C4SDA	59	PG3 (3)	I/O	OD	I ² C module 4 data.
I2C5SCL	87	PG6 (3)	I/O	OD	I ² C module 5 clock. Note that this signal has an active pull-up. The corresponding port pin should not be configured as open drain.
I2C5SDA	88	PG7 (3)	I/O	OD	I ² C module 5 data.


Table 16-1. I2C Signals (100LQFP) (continued)

16.3 Functional Description

Each I²C module is comprised of both master and slave functions and is identified by a unique address. A master-initiated communication generates the clock signal, SCL. For proper operation, the SDA pin must be configured as an open-drain signal. Due to the internal circuitry that supports high-speed operation, the SCL pin must not be configured as an open-drain signal, although the internal circuitry causes it to act as if it were an open drain signal. Both SDA and SCL signals must be connected to a positive supply voltage using a pull-up resistor. A typical I²C bus configuration is shown in Figure 16-2. Refer to the *I2C-bus specification and user manual* to determine the size of the pull-ups needed for proper operation.

See "Inter-Integrated Circuit (I²C) Interface" on page 1409 for I²C timing diagrams.

Figure 16-2. I²C Bus Configuration



16.3.1 I²C Bus Functional Overview

The I^2C bus uses only two signals: SDA and SCL, named <code>I2CSDA</code> and <code>I2CSCL</code> on Stellaris microcontrollers. SDA is the bi-directional serial data line and SCL is the bi-directional serial clock line. The bus is considered idle when both lines are High.


Every transaction on the I²C bus is nine bits long, consisting of eight data bits and a single acknowledge bit. The number of bytes per transfer (defined as the time between a valid START and STOP condition, described in "START and STOP Conditions" on page 1005) is unrestricted, but each data byte has to be followed by an acknowledge bit, and data must be transferred MSB first. When a receiver cannot receive another complete byte, it can hold the clock line SCL Low and force the transmitter into a wait state. The data transfer continues when the receiver releases the clock SCL.

a. The TTL designation indicates the pin has TTL-compatible voltage levels.

16.3.1.1 START and STOP Conditions

The protocol of the I²C bus defines two states to begin and end a transaction: START and STOP. A High-to-Low transition on the SDA line while the SCL is High is defined as a START condition, and a Low-to-High transition on the SDA line while SCL is High is defined as a STOP condition. The bus is considered busy after a START condition and free after a STOP condition. See Figure 16-3.

Figure 16-3. START and STOP Conditions




The STOP bit determines if the cycle stops at the end of the data cycle or continues on to a repeated START condition. To generate a single transmit cycle, the I^2C Master Slave Address (I2CMSA) register is written with the desired address, the R/S bit is cleared, and the Control register is written with ACK=X (0 or 1), STOP=1, START=1, and RUN=1 to perform the operation and stop. When the operation is completed (or aborted due an error), the interrupt pin becomes active and the data may be read from the I^2C Master Data (I2CMDR) register. When the I^2C module operates in Master receiver mode, the ACK bit is normally set causing the I^2C bus controller to transmit an acknowledge automatically after each byte. This bit must be cleared when the I^2C bus controller requires no further data to be transmitted from the slave transmitter.

When operating in slave mode, the STARTRIS and STOPRIS bits in the I²C Slave Raw Interrupt Status (I2CSRIS) register indicate detection of start and stop conditions on the bus and the I²C Slave Masked Interrupt Status (I2CSMIS) register can be configured to allow STARTRIS and STOPRIS to be promoted to controller interrupts (when interrupts are enabled).

16.3.1.2 Data Format with 7-Bit Address

Data transfers follow the format shown in Figure 16-4. After the START condition, a slave address is transmitted. This address is 7-bits long followed by an eighth bit, which is a data direction bit (\mathbb{R}/\mathbb{S} bit in the **I2CMSA** register). If the \mathbb{R}/\mathbb{S} bit is clear, it indicates a transmit operation (send), and if it is set, it indicates a request for data (receive). A data transfer is always terminated by a STOP condition generated by the master, however, a master can initiate communications with another device on the bus by generating a repeated START condition and addressing another slave without first generating a STOP condition. Various combinations of receive/transmit formats are then possible within a single transfer.


Figure 16-4. Complete Data Transfer with a 7-Bit Address



The first seven bits of the first byte make up the slave address (see Figure 16-5). The eighth bit determines the direction of the message. A zero in the R/S position of the first byte means that the

master transmits (sends) data to the selected slave, and a one in this position means that the master receives data from the slave.


Figure 16-5. R/S Bit in First Byte



16.3.1.3 Data Validity

The data on the SDA line must be stable during the high period of the clock, and the data line can only change when SCL is Low (see Figure 16-6).

Figure 16-6. Data Validity During Bit Transfer on the I²C Bus



16.3.1.4 Acknowledge

All bus transactions have a required acknowledge clock cycle that is generated by the master. During the acknowledge cycle, the transmitter (which can be the master or slave) releases the SDA line. To acknowledge the transaction, the receiver must pull down SDA during the acknowledge clock cycle. The data transmitted out by the receiver during the acknowledge cycle must comply with the data validity requirements described in "Data Validity" on page 1006.

When a slave receiver does not acknowledge the slave address, SDA must be left High by the slave so that the master can generate a STOP condition and abort the current transfer. If the master device is acting as a receiver during a transfer, it is responsible for acknowledging each transfer made by the slave. Because the master controls the number of bytes in the transfer, it signals the end of data to the slave transmitter by not generating an acknowledge on the last data byte. The slave transmitter must then release SDA to allow the master to generate the STOP or a repeated START condition.

If the slave is required to provide a manual ACK or NACK, the I²C Slave ACK Control (I2CSACKCTL) register allows the slave to NACK for invalid data or command or ACK for valid data or command. When this operation is enabled, the MCU slave module I²C clock is pulled low after the last data bit until this register is written with the indicated response.

16.3.1.5 Repeated Start

The I²C master module has the capability of executing a repeated START (transmit or receive) after an initial transfer has occurred.

A repeated start sequence for a Master transmit is as follows:

1. When the device is in the idle state, the Master writes the slave address to the I2CMSA register and configures the R/S bit for the desired transfer type.

- 2. Data is written to the I2CMDR register.
- 3. When the BUSY bit in the I2CMCS register is '0', the Master writes 0x3 to the I2CMCS register to initiate a transfer.
- **4.** The Master does not generate a STOP condition but instead writes another slave address to the **I2CMSA** register and then writes 0x3 to initiate the repeated START.

A repeated start sequence for a Master receive is similar:

- 1. When the device is in idle, the Master writes the slave address to the I2CMSA register and configures the R/S bit for the desired transfer type.
- 2. The master reads data from the I2CMDR register.
- 3. When the BUSY bit in the **I2CMCS** register is '0', the Master writes 0x3 to the **I2CMCS** register to initiate a transfer.
- **4.** The Master does not generate a STOP condition but instead writes another slave address to the **I2CMSA** register and then writes 0x3 to initiate the repeated START.

For more information on repeated START, refer to Figure 16-12 on page 1017 and Figure 16-13 on page 1018.

16.3.1.6 Clock Low Timeout

The I²C slave can extend the transaction by pulling the clock low periodically to create a slow bit transfer rate. The I²C module has a 12-bit programmable counter that is used to track how long the clock has been held low. The upper 8 bits of the count value are software programmable through the I²C Master Clock Low Timeout Count (I2CMCLKOCNT) register. The lower four bits are not user visible and are 0x0. The CNTL value programmed in the I2CMCLKOCNT register has to be greater than 0x01. The application can program the eight most significant bits of the counter to reflect the acceptable cumulative low period in transaction. The count is loaded at the START condition and counts down on each falling edge of the internal bus clock of the Master. Note that the internal bus clock generated for this counter keeps running at the programmed I²C speed even if SCL is held low on the bus. Upon reaching terminal count, the master state machine forces ABORT on the bus by issuing a STOP condition at the instance of SCL and SDA release.

As an example, if an I²C module was operating at 100 kHz speed, programming the **I2CMCLKOCNT** register to 0xDA would translate to the value 0xDA0 since the lower four bits are set to 0x0. This would translate to a decimal value of 3488 clocks or a cumulative clock low period of 34.88 ms at 100 kHz.

The CLKRIS bit in the I^2C Master Raw Interrupt Status (I2CMRIS) register is set when the clock timeout period is reached, allowing the master to start corrective action to resolve the remote slave state. In addition, the CLKTO bit in the I^2C Master Control/Status (I2CMCS) register is set; this bit is cleared when a STOP condition is sent or during the I^2C master reset. The status of the raw SDA and SCL signals are readable by software through the SDA and SCL bits in the I^2C Master Bus Monitor (I2CMBMON) register to help determine the state of the remote slave.

If the slave holds the clock low continuously, the Master module interrupts the processor by setting the CLKRIS bit and the application can resolve the issue at a higher protocol level by resetting both the Master and the remote slave.

Note: The Master Clock Low Timeout counter counts for the entire time SCL is held Low continuously. If SCL is de-asserted at any point, the Master Clock Low Timeout Counter is

reloaded with the value in the **I2CMCLKOCNT** register and begins counting down from this value.

16.3.1.7 Dual Address

The I^2C interface supports dual address capability for the slave. The additional programmable address is provided and can be matched if enabled. In legacy mode with dual address disabled, the I^2C slave provides an ACK on the bus if the address matches the OAR field in the I^2C slave provides an ACK on the bus if either the OAR field in the I^2C slave provides an ACK on the bus if either the OAR field in the I^2C slave provides an ACK on the bus if either the OAR field in the I^2C slave provides an ACK on the bus if either the OAR field in the I^2C slave provides an ACK on the bus if either the OAR field in the I^2C slave provides an ACK on the bus if either the OAR field in the I^2C slave provides an ACK on the bus if either the OAR field in the I^2C slave provides an ACK on the bus if either the OAR field in the I^2C slave provides an ACK on the bus if either the OAR field in the I^2C slave provides an ACK on the bus if either the OAR field in the I^2C slave provides an ACK on the bus if either the OAR field in the I^2C slave provides an ACK on the bus if either the OAR field in the I^2C slave provides an ACK on the bus if either the OAR field in the I^2C slave provides an ACK on the bus if either the OAR field in the I^2C slave provides an ACK on the I^2C slave pro

The OAR2SEL bit in the **I2CSCSR** register indicates if the address that was ACKed is the alternate address or not. When this bit is clear, it indicates either legacy operation or no address match.

16.3.1.8 Arbitration

A master may start a transfer only if the bus is idle. It's possible for two or more masters to generate a START condition within minimum hold time of the START condition. In these situations, an arbitration scheme takes place on the SDA line, while SCL is High. During arbitration, the first of the competing master devices to place a '1' (High) on SDA, while another master transmits a '0' (Low), switches off its data output stage and retires until the bus is idle again.

Arbitration can take place over several bits. Its first stage is a comparison of address bits, and if both masters are trying to address the same device, arbitration continues on to the comparison of data bits.

16.3.1.9 Glitch Suppression in Multi-Master Configuration

When a multi-master configuration is being used, the GFE bit in the I²C Master Configuration (I2CMCR) register can be set to enable glitch suppression on the SCL and SDA lines and assure proper signal values. The filter can be programmed to different filter widths using the GFPW bit in the I²C Master Configuration 2 (I2CMCR2) register. The glitch suppression value is in terms of buffered system clocks. Note that all signals will be delayed internally when glitch suppression is nonzero. For example, if GSPW is set to 0x7, 32 clocks should be added onto the calculation for the expected transaction time.

16.3.2 Available Speed Modes

The I²C bus can run in Standard mode (100 kbps), Fast mode (400 kbps), Fast mode plus (1 Mbps) or High-Speed mode (3.33 Mbps). The selected mode should match the speed of the other I²C devices on the bus.

16.3.2.1 Standard, Fast, and Fast Plus Modes

Standard, Fast, and Fast Plus modes are selected using a value in the I²C Master Timer Period (I2CMTPR) register that results in an SCL frequency of 100 kbps for Standard mode, 400 kbps for Fast mode, or 1 Mbps for Fast mode plus.

The I²C clock rate is determined by the parameters *CLK_PRD*, *TIMER_PRD*, *SCL_LP*, and *SCL_HP* where:

CLK PRD is the system clock period

SCL_LP is the low phase of SCL (fixed at 6)

SCL_HP is the high phase of SCL (fixed at 4)

TIMER_PRD is the programmed value in the **I2CMTPR** register (see page 1031). This value is determined by replacing the known variables in the equation below and solving for TIMER PRD.

The I²C clock period is calculated as follows:

```
SCL_PERIOD = 2 × (1 + TIMER_PRD) × (SCL_LP + SCL_HP) × CLK_PRD
For example:
CLK_PRD = 50 ns
TIMER_PRD = 2
SCL_LP=6
SCL_LP=4
yields a SCL frequency of:
1/SCL_PERIOD = 333 Khz
```

Table 16-2 gives examples of the timer periods that should be used to generate Standard, Fast mode, and Fast mode plus SCL frequencies based on various system clock frequencies.

Table 16-2. Examples of I²C Master Timer Period versus Speed Mode

System Clock	Timer Period	Standard Mode	Timer Period	Fast Mode	Timer Period	Fast Mode Plus
4 MHz	0x01	100 Kbps	-	-	-	-
6 MHz	0x02	100 Kbps	-	-	-	-
12.5 MHz	0x06	89 Kbps	0x01	312 Kbps	-	-
16.7 MHz	0x08	93 Kbps	0x02	278 Kbps	-	-
20 MHz	0x09	100 Kbps	0x02	333 Kbps	-	-
25 MHz	0x0C	96.2 Kbps	0x03	312 Kbps	-	-
33 MHz	0x10	97.1 Kbps	0x04	330 Kbps	-	-
40 MHz	0x13	100 Kbps	0x04	400 Kbps	0x01	1000 Kbps
50 MHz	0x18	100 Kbps	0x06	357 Kbps	0x02	833 Kbps
80 MHz	0x27	100 Kbps	0x09	400 Kbps	0x03	1000 Kbps

16.3.2.2 High-Speed Mode

The Stellaris I 2 C peripheral has support for High-speed operation as both a master and slave. High-Speed mode is configured by setting the HS bit in the I 2 C Master Control/Status (I2CMCS) register. High-Speed mode transmits data at a high bit rate with a 66.6%/33.3% duty cycle, but communication and arbitration are done at Standard, Fast mode, or Fast-mode plus speed, depending on which is selected by the user. When the HS bit in the I2CMCS register is set, current mode pull-ups are enabled.

The clock period can be selected using the equation below, but in this case, $SCL_LP=2$ and $SCL_HP=1$.

```
SCL_PERIOD = 2 × (1 + TIMER_PRD) × (SCL_LP + SCL_HP) × CLK_PRD
So for example:
CLK_PRD = 25 ns
TIMER PRD = 1
```

SCL_LP=2 SCL HP=1

yields a SCL frequency of:

1/T = 3.33 Mhz

Table 16-3 on page 1010 gives examples of timer period and system clock in High-Speed mode. Note that the HS bit in the **I2CMTPR** register needs to be set for the TPR value to be used in High-Speed mode.


Table 16-3. Examples of I²C Master Timer Period in High-Speed Mode

System Clock	Timer Period	Transmission Mode		
40 MHz	0x01	3.33 Mbps		
50 MHz	0x02	2.77 Mbps		
80 MHz	0x03	3.33 Mbps		

When operating as a master, the protocol is shown in Figure 16-7. The master is responsible for sending a master code byte in either Standard (100 Kbps) or Fast-mode (400 Kbps) before it begins transferring in High-speed mode. The master code byte must contain data in the form of 0000.1XXX and is used to tell the slave devices to prepare for a High-speed transfer. The master code byte should never be acknowledged by a slave since it is only used to indicate that the upcoming data is going to be transferred at a higher data rate. To send the master code byte, software should place the value of the master code byte into the **I2CMSA** register and write the **I2CMCS** register with a value of 0x13. This places the I²C master peripheral in High-speed mode, and all subsequent transfers (until STOP) are carried out at High-speed data rate using the normal **I2CMCS** command bits, without setting the HS bit in the **I2CMCS** register. Again, setting the HS bit in the **I2CMCS** register is only necessary during the master code byte.

When operating as a High-speed slave, there is no additional software required.

Figure 16-7. High-Speed Data Format



Note: High-Speed mode is 3.4 Mbps, provided correct system clock frequency is set and there is appropriate pull strength on SCL and SDA lines.

16.3.3 Interrupts

The I²C can generate interrupts when the following conditions are observed:

- Master transaction completed
- Master arbitration lost
- Master transaction error

- Master bus timeout
- Slave transaction received
- Slave transaction requested
- Stop condition on bus detected
- Start condition on bus detected

The I²C master and I²C slave modules have separate interrupt signals. While both modules can generate interrupts for multiple conditions, only a single interrupt signal is sent to the interrupt controller.

16.3.3.1 I²C Master Interrupts

The I^2C master module generates an interrupt when a transaction completes (either transmit or receive), when arbitration is lost, or when an error occurs during a transaction. To enable the I^2C master interrupt, software must set the IM bit in the I^2C Master Interrupt Mask (I2CMIMR) register. When an interrupt condition is met, software must check the ERROR and ARBLST bits in the I^2C Master Control/Status (I2CMCS) register to verify that an error didn't occur during the last transaction and to ensure that arbitration has not been lost. An error condition is asserted if the last transaction wasn't acknowledged by the slave. If an error is not detected and the master has not lost arbitration, the application can proceed with the transfer. The interrupt is cleared by writing a 1 to the IC bit in the I^2C Master Interrupt Clear (I2CMICR) register.

If the application doesn't require the use of interrupts, the raw interrupt status is always visible via the I^2C Master Raw Interrupt Status (I2CMRIS) register.

16.3.3.2 I²C Slave Interrupts

The slave module can generate an interrupt when data has been received or requested. This interrupt is enabled by setting the DATAIM bit in the I^2C Slave Interrupt Mask (I2CSIMR) register. Software determines whether the module should write (transmit) or read (receive) data from the I^2C Slave Data (I2CSDR) register, by checking the RREQ and TREQ bits of the I^2C Slave Control/Status (I2CSCSR) register. If the slave module is in receive mode and the first byte of a transfer is received, the FBR bit is set along with the RREQ bit. The interrupt is cleared by setting the DATAIC bit in the I^2C Slave Interrupt Clear (I2CSICR) register.

In addition, the slave module can generate an interrupt when a start and stop condition is detected. These interrupts are enabled by setting the STARTIM and STOPIM bits of the I²C Slave Interrupt Mask (I2CSIMR) register and cleared by writing a 1 to the STOPIC and STARTIC bits of the I²C Slave Interrupt Clear (I2CSICR) register.

If the application doesn't require the use of interrupts, the raw interrupt status is always visible via the I²C Slave Raw Interrupt Status (I2CSRIS) register.

16.3.4 Loopback Operation

The I²C modules can be placed into an internal loopback mode for diagnostic or debug work by setting the LPBK bit in the I²C Master Configuration (I2CMCR) register. In loopback mode, the SDA and SCL signals from the master and are tied to the SDA and SCL signals of the slave module to allow internal testing of the device without having to go through I/O.

16.3.5 Command Sequence Flow Charts

This section details the steps required to perform the various I^2C transfer types in both master and slave mode.

16.3.5.1 I²C Master Command Sequences

The figures that follow show the command sequences available for the I²C master.




Figure 16-8. Master Single TRANSMIT




Figure 16-9. Master Single RECEIVE




Figure 16-10. Master TRANSMIT of Multiple Data Bytes




Figure 16-11. Master RECEIVE of Multiple Data Bytes




Figure 16-12. Master RECEIVE with Repeated START after Master TRANSMIT

February 20, 2013 1017




Figure 16-13. Master TRANSMIT with Repeated START after Master RECEIVE





Figure 16-14. High Speed Mode Master Transmit

16.3.5.2 I²C Slave Command Sequences

Figure 16-15 on page 1020 presents the command sequence available for the I²C slave.

Figure 16-15. Slave Command Sequence



16.4 Initialization and Configuration

The following example shows how to configure the I²C module to transmit a single byte as a master. This assumes the system clock is 20 MHz.

- 1. Enable the I²C clock using the **RCGCI2C** register in the System Control module (see page 339).
- 2. Enable the clock to the appropriate GPIO module via the **RCGCGPIO** register in the System Control module (see page 330). To find out which GPIO port to enable, refer to Table 23-5 on page 1367.
- 3. In the GPIO module, enable the appropriate pins for their alternate function using the **GPIOAFSEL** register (see page 670). To determine which GPIOs to configure, see Table 23-4 on page 1358.
- **4.** Enable the I2CSDA pin for open-drain operation. See page 675.

- **5.** Configure the PMCn fields in the **GPIOPCTL** register to assign the I²C signals to the appropriate pins. See page 688 and Table 23-5 on page 1367.
- **6.** Initialize the I²C Master by writing the **I2CMCR** register with a value of 0x0000.0010.
- 7. Set the desired SCL clock speed of 100 Kbps by writing the **I2CMTPR** register with the correct value. The value written to the **I2CMTPR** register represents the number of system clock periods in one SCL clock period. The TPR value is determined by the following equation:

```
TPR = (System Clock/(2*(SCL_LP + SCL_HP)*SCL_CLK))-1;
TPR = (20MHz/(2*(6+4)*100000))-1;
TPR = 9
```

Write the **I2CMTPR** register with the value of 0x0000.0009.

- **8.** Specify the slave address of the master and that the next operation is a Transmit by writing the **I2CMSA** register with a value of 0x0000.0076. This sets the slave address to 0x3B.
- Place data (byte) to be transmitted in the data register by writing the I2CMDR register with the desired data.
- **10.** Initiate a single byte transmit of the data from Master to Slave by writing the **I2CMCS** register with a value of 0x0000.0007 (STOP, START, RUN).
- 11. Wait until the transmission completes by polling the I2CMCS register's BUSBSY bit until it has been cleared.
- 12. Check the ERROR bit in the I2CMCS register to confirm the transmit was acknowledged.

To configure the I²C master to High Speed mode:

- 1. Enable the I²C clock using the **RCGCI2C** register in the System Control module (see page 339).
- 2. Enable the clock to the appropriate GPIO module via the **RCGCGPIO** register in the System Control module (see page 330). To find out which GPIO port to enable, refer to Table 23-5 on page 1367.
- 3. In the GPIO module, enable the appropriate pins for their alternate function using the **GPIOAFSEL** register (see page 670). To determine which GPIOs to configure, see Table 23-4 on page 1358.
- 4. Enable the I2CSDA pin for open-drain operation. See page 675.
- **5.** Configure the PMCn fields in the **GPIOPCTL** register to assign the I²C signals to the appropriate pins. See page 688 and Table 23-5 on page 1367.
- **6.** Initialize the I²C Master by writing the **I2CMCR** register with a value of 0x0000.0010.
- 7. Set the desired SCL clock speed of 100 Kbps by writing the **I2CMTPR** register with the correct value. The value written to the **I2CMTPR** register represents the number of system clock periods in one SCL clock period. The TPR value is determined by the following equation:

```
TPR = (System Clock/(2*(SCL_LP + SCL_HP)*SCL_CLK))-1;
TPR = (80 MHz/(2*(2+1)*3330000))-1;
TPR = 3
```

Write the **I2CMTPR** register with the value of 0x0000.0003.

- **8.** To send the master code byte, software should place the value of the master code byte into the **I2CMSA** register and write the **I2CMCS** register with a value of 0x13.
- **9.** This places the I2C master peripheral in High-speed mode, and all subsequent transfers (until STOP) are carried out at High-speed data rate using the normal **I2CMCS** command bits, without setting the HS bit in the **I2CMCS** register.
- **10.** The transaction is ended by setting the STOP bit in the **I2CMCS** register.
- 11. Wait until the transmission completes by polling the I2CMCS register's BUSBSY bit until it has been cleared.
- 12. Check the ERROR bit in the I2CMCS register to confirm the transmit was acknowledged.

16.5 Register Map

Table 16-4 on page 1022 lists the I²C registers. All addresses given are relative to the I²C base address:

■ I²C 0: 0x4002.0000

■ I²C 1: 0x4002.1000

■ I²C 2: 0x4002.2000

■ I²C 3: 0x4002.3000

■ I²C 4: 0x400C.0000

■ I²C 5: 0x400C.1000

Note that the I²C module clock must be enabled before the registers can be programmed (see page 339). There must be a delay of 3 system clocks after the I²C module clock is enabled before any I²C module registers are accessed.

The hw_i2c.h file in the StellarisWare[®] Driver Library uses a base address of 0x800 for the I²C slave registers. Be aware when using registers with offsets between 0x800 and 0x818 that StellarisWare uses an offset between 0x000 and 0x018 with the slave base address.

Table 16-4. Inter-Integrated Circuit (I²C) Interface Register Map

Offset	Name	Туре	Reset	Description	See page
I ² C Maste	r				·
0x000	I2CMSA	R/W	0x0000.0000	I2C Master Slave Address	1024
0x004	I2CMCS	R/W	0x0000.0020	I2C Master Control/Status	1025
0x008	I2CMDR	R/W	0x0000.0000	I2C Master Data	1030
0x00C	I2CMTPR	R/W	0x0000.0001	I2C Master Timer Period	1031
0x010	I2CMIMR	R/W	0x0000.0000	I2C Master Interrupt Mask	1032
0x014	I2CMRIS	RO	0x0000.0000	I2C Master Raw Interrupt Status	1033
0x018	I2CMMIS	RO	0x0000.0000	I2C Master Masked Interrupt Status	1034
0x01C	I2CMICR	WO	0x0000.0000	I2C Master Interrupt Clear	1035
0x020	I2CMCR	R/W	0x0000.0000	I2C Master Configuration	1036

Table 16-4. Inter-Integrated Circuit (I²C) Interface Register Map (continued)

Offset	Name	Туре	Reset	Description	See page
0x024	12CMCLKOCNT	R/W	0x0000.0000	I2C Master Clock Low Timeout Count	1038
0x02C	I2CMBMON	RO	0x0000.0003	I2C Master Bus Monitor	1039
0x038	I2CMCR2	RO	0x0000.0000	I2C Master Configuration 2	1040
I ² C Slave					·
0x800	I2CSOAR	R/W	0x0000.0000	I2C Slave Own Address	1041
0x804	I2CSCSR	RO	0x0000.0000	I2C Slave Control/Status	1042
0x808	I2CSDR	R/W	0x0000.0000	I2C Slave Data	1044
0x80C	I2CSIMR	R/W	0x0000.0000	I2C Slave Interrupt Mask	1045
0x810	I2CSRIS	RO	0x0000.0000	I2C Slave Raw Interrupt Status	1046
0x814	I2CSMIS	RO	0x0000.0000	I2C Slave Masked Interrupt Status	1047
0x818	I2CSICR	WO	0x0000.0000	I2C Slave Interrupt Clear	1048
0x81C	I2CSOAR2	R/W	0x0000.0000	I2C Slave Own Address 2	1049
0x820	I2CSACKCTL	R/W	0x0000.0000	I2C Slave ACK Control	1050
I ² C Status	and Control				1
0xFC0	I2CPP	RO	0x0000.0001	I2C Peripheral Properties	1051
0xFC4	I2CPC	RO	0x0000.0001	I2C Peripheral Configuration	1052

16.6 Register Descriptions (I²C Master)

The remainder of this section lists and describes the I^2C master registers, in numerical order by address offset.


Register 1: I²C Master Slave Address (I2CMSA), offset 0x000

This register consists of eight bits: seven address bits (A6-A0), and a Receive/Send bit, which determines if the next operation is a Receive (High), or Transmit (Low).

I2C Master Slave Address (I2CMSA)

I2C 0 base: 0x4002.0000 I2C 1 base: 0x4002.1000 I2C 2 base: 0x4002.2000 I2C 3 base: 0x4002.3000 I2C 4 base: 0x400C.0000 I2C 5 base: 0x400C.1000 Offset 0x000

Type R/W, reset 0x0000.0000



Bit/Field	Name	Туре	Reset	Description
31:8	reserved	RO	0x0000.00	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
7:1	SA	R/W	0x00	I ² C Slave Address This field specifies bits A6 through A0 of the slave address.
0	R/S	R/W	0	Receive/Send The R/S bit specifies if the next operation is a Receive (High) or Transmit

(Low).

Value Description

0 Transmit

1 Receive

Register 2: I²C Master Control/Status (I2CMCS), offset 0x004

This register accesses status bits when read and control bits when written. When read, the status register indicates the state of the I^2C bus controller. When written, the control register configures the I^2C controller operation.

The START bit generates the START or REPEATED START condition. The STOP bit determines if the cycle stops at the end of the data cycle or continues to the next transfer cycle, which could be a repeated START. To generate a single transmit cycle, the I^2C Master Slave Address (I2CMSA) register is written with the desired address, the R/S bit is cleared, and this register is written with ACK=X (0 or 1), STOP=1, START=1, and RUN=1 to perform the operation and stop. When the operation is completed (or aborted due an error), an interrupt becomes active and the data may be read from the I2CMDR register. When the I^2C module operates in Master receiver mode, the ACK bit is normally set, causing the I^2C bus controller to transmit an acknowledge automatically after each byte. This bit must be cleared when the I^2C bus controller requires no further data to be transmitted from the slave transmitter.

Read-Only Status Register


I2C Master Control/Status (I2CMCS)

I2C 0 base: 0x4002.0000 I2C 1 base: 0x4002.1000 I2C 2 base: 0x4002.2000 I2C 3 base: 0x4002.3000 I2C 4 base: 0x400C.0000

I2C 5 base: 0x400C.1000

Offset 0x004

Type RO, reset 0x0000.0020



Bit/Field	Name	Type	Reset	Description
31:8	reserved	RO	0x0000.00	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
7	CLKTO	RO	0	Clock Timeout Error

Value Description

- 0 No clock timeout error.
- 1 The clock timeout error has occurred.

This bit is cleared when the master sends a STOP condition or if the I^2C master is reset.

Bit/Field	Name	Туре	Reset	Description
6	BUSBSY	RO	0	Bus Busy
				Value Description The I ² C bus is idle. The I ² C bus is busy. The bit changes based on the START and STOP conditions.
5	IDLE	RO	1	I ² C Idle
				Value Description The I ² C controller is not idle. The I ² C controller is idle.
4	ARBLST	RO	0	Arbitration Lost
				 Value Description The I²C controller won arbitration. The I²C controller lost arbitration.
3	DATACK	RO	0	Acknowledge Data
				Value Description The transmitted data was acknowledged The transmitted data was not acknowledged.
2	ADRACK	RO	0	Acknowledge Address
				Value Description The transmitted address was acknowledged The transmitted address was not acknowledged.
1	ERROR	RO	0	Error
				Value Description No error was detected on the last operation. An error occurred on the last operation. The error can be from the slave address not being acknowledged or the transmit data not being acknowledged.
0	BUSY	RO	0	Value Description The controller is idle. The controller is busy. When the BUSY bit is set, the other status bits are not valid.

Write-Only Control Register

I2C Master Control/Status (I2CMCS)

I2C 0 base: 0x4002.0000 I2C 1 base: 0x4002.1000 I2C 2 base: 0x4002.2000 I2C 3 base: 0x4002.3000 I2C 4 base: 0x400C.0000 I2C 5 base: 0x400C.1000 Offset 0x004

Offset 0x004 Type WO, reset 0x0000.0020

	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16
								rese	rved							
Type Reset	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0
	15	14	13	12	11	10	9	8	7	6	5	4	3	2	1	0
		'				reserved						HS	ACK	STOP	START	RUN
Type Reset	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	WO 0	WO 0	WO 0	WO 0	WO 0

Bit/Field	Name	Туре	Reset	Description
31:5	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
4	HS	WO	0	High-Speed Enable
				Value Description
				The master operates in Standard, Fast mode, or Fast mode plus as selected by using a value in the I2CMTPR register that results in an SCL frequency of 100 kbps for Standard mode, 400 kbps for Fast mode, or 1 Mpbs for Fast mode plus.
				1 The master operates in High-Speed mode with transmission speeds up to 3.33 Mbps.
3	ACK	WO	0	Data Acknowledge Enable
				Value Description
				The received data byte is not acknowledged automatically by the master.
				1 The received data byte is acknowledged automatically by the master. See field decoding in Table 16-5 on page 1028.
2	STOP	WO	0	Generate STOP

Value Description

- 0 The controller does not generate the STOP condition.
- 1 The controller generates the STOP condition. See field decoding in Table 16-5 on page 1028.

Bit/Field	Name	Type	Reset	Description
1	START	WO	0	Generate START
				Value Description
				0 The controller does not generate the START condition.
				1 The controller generates the START or repeated START condition. See field decoding in Table 16-5 on page 1028.
0	RUN	WO	0	I ² C Master Enable

Value Description

- 0 The master is disabled.
- 1 The master is enabled to transmit or receive data. See field decoding in Table 16-5 on page 1028.

Table 16-5. Write Field Decoding for I2CMCS[3:0] Field

Current	t				Description	
State	R/S	ACK	STOP	START	RUN	Description
	0	X ^a	0	1	1	START condition followed by TRANSMIT (master goes to the Master Transmit state).
	0	Х	1	1	1	START condition followed by a TRANSMIT and STOP condition (master remains in Idle state).
Lalla	1	0	0	1	1	START condition followed by RECEIVE operation with negative ACK (master goes to the Master Receive state).
Idle	1	0	1	1	1	START condition followed by RECEIVE and STOP condition (master remains in Idle state).
	1	1	0	1	1	START condition followed by RECEIVE (master goes to the Master Receive state).
	1	1	1	1	1	Illegal
	All other co	mbinations	s not listed	are non-op	erations.	NOP
	Х	Х	0	0	1	TRANSMIT operation (master remains in Master Transmit state).
	Х	Х	1	0	0	STOP condition (master goes to Idle state).
	Х	Х	1	0	1	TRANSMIT followed by STOP condition (master goes to Idle state).
	0	Х	0	1	1	Repeated START condition followed by a TRANSMIT (master remains in Master Transmit state).
Master	0	Х	1	1	1	Repeated START condition followed by TRANSMIT and STOP condition (master goes to Idle state).
Transmit	1	0	0	1	1	Repeated START condition followed by a RECEIVE operation with a negative ACK (master goes to Master Receive state).
	1	0	1	1	1	Repeated START condition followed by a TRANSMIT and STOP condition (master goes to Idle state).
	1	1	0	1	1	Repeated START condition followed by RECEIVE (master goes to Master Receive state).
	1	1	1	1	1	Illegal.
	All other co	mbinations	s not listed	are non-op	erations.	NOP.

Table 16-5. Write Field Decoding for I2CMCS[3:0] Field (continued)

Current	12CMSA[0] 12CMCS[3:0]					Description
State	R/S	ACK	STOP	START	RUN	Description
	Х	0	0	0	1	RECEIVE operation with negative ACK (master remains in Master Receive state).
	Х	Х	1	0	0	STOP condition (master goes to Idle state).b
	Х	0	1	0	1	RECEIVE followed by STOP condition (master goes to Idle state).
	Х	1	0	0	1	RECEIVE operation (master remains in Master Receive state).
	Х	1	1	0	1	Illegal.
Master Receive	1	0	0	1	1	Repeated START condition followed by RECEIVE operation with a negative ACK (master remains in Master Receive state).
	1	0	1	1	1	Repeated START condition followed by RECEIVE and STOP condition (master goes to Idle state).
	1	1	0	1	1	Repeated START condition followed by RECEIVE (master remains in Master Receive state).
	0	Х	0	1	1	Repeated START condition followed by TRANSMIT (master goes to Master Transmit state).
	0	Х	1	1	1	Repeated START condition followed by TRANSMIT and STOP condition (master goes to Idle state).
	All other co	mbinations	s not listed	are non-op	erations.	NOP.

a. An X in a table cell indicates the bit can be 0 or 1.

b. In Master Receive mode, a STOP condition should be generated only after a Data Negative Acknowledge executed by the master or an Address Negative Acknowledge executed by the slave.

Register 3: I²C Master Data (I2CMDR), offset 0x008

Important: This register is read-sensitive. See the register description for details.

This register contains the data to be transmitted when in the Master Transmit state and the data received when in the Master Receive state.


I2C Master Data (I2CMDR)

I2C 0 base: 0x4002.0000 I2C 1 base: 0x4002.1000 I2C 2 base: 0x4002.2000 I2C 3 base: 0x4002.3000

I2C 4 base: 0x400C.0000 I2C 5 base: 0x400C.1000

Offset 0x008

Type R/W, reset 0x0000.0000



Bit/Field	Name	Type	Reset	Description
31:8	reserved	RO	0x0000.00	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
7:0	DATA	R/W	0x00	This byte contains the data transferred during a transaction.

Register 4: I²C Master Timer Period (I2CMTPR), offset 0x00C


This register is programmed to set the timer period for the SCL clock and assign the SCL clock to either standard or high-speed mode.

I2C Master Timer Period (I2CMTPR)

I2C 0 base: 0x4002.0000 I2C 1 base: 0x4002.1000 I2C 2 base: 0x4002.2000 I2C 3 base: 0x4002.3000 I2C 4 base: 0x400C.0000 I2C 5 base: 0x400C.1000

Offset 0x00C

Type R/W, reset 0x0000.0001



Bit/Field	Name	Type	Reset	Description
31:8	reserved	RO	0x0000.00	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
7	HS	WO	0x0	High-Speed Enable
				Value Description
				The SCL Clock Period set by TPR applies to Standard mode (100 Kbps), Fast-mode (400 Kbps), or Fast-mode plus (1 Mbps).
				1 The SCL Clock Period set by TPR applies to High-speed mode (3.33 Mbps).
6:0	TPR	R/W	0x1	Timer Period

This field is used in the equation to configure SCL_PERIOD : $SCL_PERIOD = 2 \times (1 + TPR) \times (SCL_LP + SCL_HP) \times CLK_PRD$

where:

SCL_PRD is the SCL line period (I²C clock).

 $\ensuremath{\mathtt{TPR}}$ is the Timer Period register value (range of 1 to 127).

 SCL_LP is the SCL Low period (fixed at 6).

SCL_HP is the SCL High period (fixed at 4).

 $\mathit{CLK}_\mathit{PRD}$ is the system clock period in ns.

Register 5: I²C Master Interrupt Mask (I2CMIMR), offset 0x010

This register controls whether a raw interrupt is promoted to a controller interrupt.

I2C Master Interrupt Mask (I2CMIMR)

I2C 0 base: 0x4002.0000 I2C 1 base: 0x4002.1000 I2C 2 base: 0x4002.2000 I2C 3 base: 0x4002.3000 I2C 4 base: 0x400C.0000 I2C 5 base: 0x400C.1000 Offset 0x010

Type R/W, reset 0x0000.0000

	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16
		1		1				rese	rved						1	
Type Reset	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0
	15	14	13	12	11	10	9	8	7	6	5	4	3	2	1	0
	'	' '		•		reserved								CLKIM	IM	
Type Reset	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	R/W 0	R/W 0

Bit/Field	Name	Type	Reset	Description
31:2	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
1	CLKIM	R/W	0	Clock Timeout Interrupt Mask
				Value Description
				O The CLKRIS interrupt is suppressed and not sent to the interrupt controller.
				1 The clock timeout interrupt is sent to the interrupt controller when the CLKRIS bit in the I2CMRIS register is set.
0	IM	R/W	0	Master Interrupt Mask

Value Description

- The RIS interrupt is suppressed and not sent to the interrupt controller.
- The master interrupt is sent to the interrupt controller when the RIS bit in the **I2CMRIS** register is set.


Register 6: I²C Master Raw Interrupt Status (I2CMRIS), offset 0x014

This register specifies whether an interrupt is pending.

I2C Master Raw Interrupt Status (I2CMRIS)

I2C 0 base: 0x4002.0000 I2C 1 base: 0x4002.1000 I2C 2 base: 0x4002.2000 I2C 3 base: 0x4002.3000 I2C 4 base: 0x400C.0000 I2C 5 base: 0x400C.1000 Offset 0x014

Type RO, reset 0x0000.0000



Bit/Field	Name	Type	Reset	Description
31:2	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
1	CLKRIS	RO	0	Clock Timeout Raw Interrupt Status
				Value Description
				0 No interrupt.
				1 The clock timeout interrupt is pending.
				This bit is cleared by writing a 1 to the CLKIC bit in the $\mbox{{\tt I2CMICR}}$ register.
0	RIS	RO	0	Master Raw Interrupt Status

Value Description

0 No interrupt.

1 A master interrupt is pending.

This bit is cleared by writing a 1 to the IC bit in the I2CMICR register.


Register 7: I²C Master Masked Interrupt Status (I2CMMIS), offset 0x018

This register specifies whether an interrupt was signaled.

I2C Master Masked Interrupt Status (I2CMMIS)

I2C 0 base: 0x4002.0000 I2C 1 base: 0x4002.1000 I2C 2 base: 0x4002.2000 I2C 3 base: 0x4002.3000 I2C 4 base: 0x400C.0000 I2C 5 base: 0x400C.1000 Offset 0x018

Type RO, reset 0x0000.0000



Bit/Field	Name	Туре	Reset	Description
31:2	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
1	CLKMIS	RO	0	Clock Timeout Masked Interrupt Status
				Value Description
				0 No interrupt.
				An unmasked clock timeout interrupt was signaled and is pending.
				This bit is cleared by writing a 1 to the CLKIC bit in the I2CMICR register.
0	MIS	RO	0	Masked Interrupt Status

Value Description

- 0 An interrupt has not occurred or is masked.
- 1 An unmasked master interrupt was signaled and is pending.

This bit is cleared by writing a 1 to the IC bit in the I2CMICR register.


Register 8: I²C Master Interrupt Clear (I2CMICR), offset 0x01C

This register clears the raw and masked interrupts.

I2C Master Interrupt Clear (I2CMICR)

I2C 0 base: 0x4002.0000 I2C 1 base: 0x4002.1000 I2C 2 base: 0x4002.2000 I2C 3 base: 0x4002.3000 I2C 4 base: 0x400C.0000 I2C 5 base: 0x400C.1000 Offset 0x01C

Type WO, reset 0x0000.0000



Bit/Field	Name	Type	Reset	Description
31:2	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
1	CLKIC	WO	0	Clock Timeout Interrupt Clear
				Writing a 1 to this bit clears the CLKRIS bit in the I2CMRIS register and the CLKMIS bit in the I2CMMIS register.
				A read of this register returns no meaningful data.
0	IC	WO	0	Master Interrupt Clear
				Westing a 4 to this bit along the page bit in the LOOKER and interested the

Writing a 1 to this bit clears the RIS bit in the I2CMRIS register and the MIS bit in the I2CMMIS register.

A read of this register returns no meaningful data.

Register 9: I²C Master Configuration (I2CMCR), offset 0x020

This register configures the mode (Master or Slave), enables the glitch filter, and sets the interface for test mode loopback.

I2C Master Configuration (I2CMCR)

I2C 0 base: 0x4002.0000
I2C 1 base: 0x4002.1000
I2C 2 base: 0x4002.2000
I2C 2 base: 0x4002.3000
I2C 3 base: 0x4002.3000
I2C 4 base: 0x400C.0000
I2C 5 base: 0x400C.1000
Offset 0x020
Type R/W, reset 0x0000.0000

	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16
		1	1					rese	rved					'		
Type Reset	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0
_	15	14	13	12	11	10	9	8	7	6	5	4	3	2	1	0
		1	1		reserved			1		GFE	SFE	MFE		reserved		LPBK
Type Reset	RO	RO	RO	RO	RO	RO 0	RO	RO	RO	R/W	R/W	R/W 0	RO 0	RO	RO	R/W
Reset	U	U	U	U	U	U	U	U	U	U	U	U	U	U	U	U

Bit/Field	Name	Туре	Reset	Description
31:7	reserved	RO	0x0000.00	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
6	GFE	R/W	0	I ² C Glitch Filter Enable
				Value Description 0 I ² C glitch filter is disabled. 1 I ² C glitch filter is enabled.
				Use the GFPW bit in the I ² C Master Configuration 2 (I2CMCR2) register to program the pulse width.
5	SFE	R/W	0	I ² C Slave Function Enable
				Value Description Slave mode is disabled. Slave mode is enabled.
4	MFE	R/W	0	I ² C Master Function Enable
				Value Description 0 Master mode is disabled. 1 Master mode is enabled.
3:1	reserved	RO	0x0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.

Bit/Field	Name	Туре	Reset	Description
0	LPBK	R/W	0	I ² C Loopback
				Value Description
				0 Normal operation.
				1 The controller in a test mode loophack configuration

February 20, 2013 1037

Register 10: I²C Master Clock Low Timeout Count (I2CMCLKOCNT), offset 0x024


This register contains the upper 8 bits of a 12-bit counter that can be used to keep the timeout limit for clock stretching by a remote slave. The lower four bits of the counter are not user visible and are always 0x0.

Note: The Master Clock Low Timeout counter counts for the entire time SCL is held Low continuously. If SCL is de-asserted at any point, the Master Clock Low Timeout Counter is reloaded with the value in the **I2CMCLKOCNT** register and begins counting down from this value.

I2C Master Clock Low Timeout Count (I2CMCLKOCNT)

I2C 0 base: 0x4002.0000 I2C 1 base: 0x4002.1000 I2C 2 base: 0x4002.2000 I2C 3 base: 0x4002.3000 I2C 4 base: 0x400C.0000 I2C 5 base: 0x400C.1000

Offset 0x024 Type R/W, reset 0x0000.0000



Bit/Field	Name	Type	Reset	Description
31:8	reserved	RO	0x0000.00	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
7:0	CNTL	R/W	0	I ² C Master Count

This field contains the upper 8 bits of a 12-bit counter for the clock low timeout count.

Note: The value of CNTL must be greater than 0x1.


Register 11: I²C Master Bus Monitor (I2CMBMON), offset 0x02C

This register is used to determine the SCL and SDA signal status.

I2C Master Bus Monitor (I2CMBMON)

I2C 0 base: 0x4002.0000 I2C 1 base: 0x4002.1000 I2C 2 base: 0x4002.2000 I2C 3 base: 0x4002.3000 I2C 4 base: 0x400C.0000 I2C 5 base: 0x400C.1000 Offset 0x02C

Type RO, reset 0x0000.0003



Bit/Field	Name	Type	Reset	Description
31:2	reserved	RO	0x0000.000	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
1	SDA	RO	1	I ² C SDA Status
				Value Description
				0 The I2CSDA signal is low.
				1 The I2CSDA signal is high.
0	SCL	RO	1	I ² C SCL Status

Value Description

0 The I2CSCL signal is low.

1 The I2CSCL signal is high.

Register 12: I²C Master Configuration 2 (I2CMCR2), offset 0x038

This register can be programmed to select the pulse width for glitch suppression, measured in system clocks.

I2C Master Configuration 2 (I2CMCR2)


Namo

I2C 0 base: 0x4002.0000 I2C 1 base: 0x4002.1000 I2C 2 base: 0x4002.2000 I2C 3 base: 0x4002.3000 I2C 4 base: 0x400C.0000 I2C 5 base: 0x400C.1000 Offset 0x038

Type RO, reset 0x0000.0000

Dit/Eiold

3:0



Docot

Divi ielu	IName	Type	Neset	Description
31:7	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
6.4	GFPW	RO	0	I ² C. Glitch Filter Pulse Width

Description

This field controls the pulse width select for glitch suppression on the SCL and SDA lines. Glitch suppression values can be programmed relative to system clocks.

Value Description 0x0 **Bypass** 0x1 1 clock 0x2 2 clocks 0x3 3 clocks 4 clocks 0x4 0x5 8 clocks 0x6 16 clocks 0x7 32 clocks

Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.

16.7 Register Descriptions (I²C Slave)

RO

reserved

The remainder of this section lists and describes the I²C slave registers, in numerical order by address offset.


Register 13: I²C Slave Own Address (I2CSOAR), offset 0x800

This register consists of seven address bits that identify the Stellaris I²C device on the I²C bus.

I2C Slave Own Address (I2CSOAR)

I2C 0 base: 0x4002.0000 I2C 1 base: 0x4002.1000 I2C 2 base: 0x4002.2000 I2C 3 base: 0x4002.3000 I2C 4 base: 0x400C.0000 I2C 5 base: 0x400C.1000 Offset 0x800

Type R/W, reset 0x0000.0000



Bit/Field	name	туре	Reset	Description
31:7	reserved	RO	0x0000.00	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
6:0	OAR	R/W	0x00	I ² C Slave Own Address

This field specifies bits A6 through A0 of the slave address.

Register 14: I²C Slave Control/Status (I2CSCSR), offset 0x804


This register functions as a control register when written, and a status register when read.

Read-Only Status Register

I2C Slave Control/Status (I2CSCSR)

I2C 0 base: 0x4002.0000 I2C 1 base: 0x4002.1000 I2C 2 base: 0x4002.2000 I2C 3 base: 0x4002.3000 I2C 4 base: 0x400C.0000 I2C 5 base: 0x400C.1000 Offset 0x804

Type RO, reset 0x0000.0000



Bit/Field	Name	Type	Reset	Description
31:4	reserved	RO	0x0000.000	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
3	OAR2SEL	RO	0	OAR2 Address Matched
				Value Description
				6 Either the address is not matched or the match is in legacy mode.
				1 OAR2 address matched and ACKed by the slave.
				This bit gets reevaluated after every address comparison.
2	FBR	RO	0	First Byte Received
				Value Description

0 The first byte has not been received.

The first byte following the slave's own address has been received.

This bit is only valid when the $\tt RREQ$ bit is set and is automatically cleared when data has been read from the <code>I2CSDR</code> register.

Note: This bit is not used for slave transmit operations.

Bit/Field	Name	Type	Reset	Description
1	TREQ	RO	0	Transmit Request
				Value Description
				0 No outstanding transmit request.
				The I ² C controller has been addressed as a slave transmitter and is using clock stretching to delay the master until data has been written to the I2CSDR register.
0	RREQ	RO	0	Receive Request

Value Description

- 0 No outstanding receive data.
- The I²C controller has outstanding receive data from the I²C master and is using clock stretching to delay the master until the data has been read from the I2CSDR register.


Write-Only Control Register

I2C Slave Control/Status (I2CSCSR)

I2C 0 base: 0x4002.0000 I2C 1 base: 0x4002.1000 I2C 2 base: 0x4002.2000 I2C 3 base: 0x4002.3000 I2C 4 base: 0x400C.0000 I2C 5 base: 0x400C.1000

Offset 0x804

Type WO, reset 0x0000.0000



Bit/Field	Name	Type	Reset	Description
31:1	reserved	RO	0x0000.000	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
0	DA	WO	0	Device Active

Value Description

- 0 Disables the I²C slave operation.
- 1 Enables the I²C slave operation.

Once this bit has been set, it should not be set again unless it has been cleared by writing a 0 or by a reset, otherwise transfer failures may occur.

Register 15: I²C Slave Data (I2CSDR), offset 0x808


Important: This register is read-sensitive. See the register description for details.

This register contains the data to be transmitted when in the Slave Transmit state, and the data received when in the Slave Receive state.

I2C Slave Data (I2CSDR)

I2C 0 base: 0x4002.0000 I2C 1 base: 0x4002.1000 I2C 2 base: 0x4002.2000 I2C 3 base: 0x4002.3000 I2C 4 base: 0x400C.0000 I2C 5 base: 0x400C.1000

Offset 0x808 Type R/W, reset 0x0000.0000



Bit/Field	Name	Type	Reset	Description
31:8	reserved	RO	0x0000.00	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
7:0	DATA	R/W	0x00	Data for Transfer

This field contains the data for transfer during a slave receive or transmit operation.


Register 16: I²C Slave Interrupt Mask (I2CSIMR), offset 0x80C

This register controls whether a raw interrupt is promoted to a controller interrupt.

I2C Slave Interrupt Mask (I2CSIMR)

I2C 0 base: 0x4002.0000 I2C 1 base: 0x4002.1000 I2C 2 base: 0x4002.2000 I2C 3 base: 0x4002.3000 I2C 4 base: 0x400C.0000 I2C 5 base: 0x400C.1000 Offset 0x80C

Type R/W, reset 0x0000.0000



Bit/Field	Name	Type	Reset	Description
Dier ioid	ranio	.,,,,	110001	20001111011
31:3	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
2	STOPIM	R/W	0	Stop Condition Interrupt Mask
				Value Description
				O The STOPRIS interrupt is suppressed and not sent to the interrupt controller.
				1 The STOP condition interrupt is sent to the interrupt controller when the STOPRIS bit in the I2CSRIS register is set.
1	STARTIM	R/W	0	Start Condition Interrupt Mask
				Value Description
				0 The STARTRIS interrupt is suppressed and not sent to the interrupt controller.
				1 The START condition interrupt is sent to the interrupt controller when the STARTRIS bit in the I2CSRIS register is set.
0	DATAIM	R/W	0	Data Interrupt Mask

Value Description

- The DATARIS interrupt is suppressed and not sent to the interrupt controller.
- The data received or data requested interrupt is sent to the interrupt controller when the DATARIS bit in the I2CSRIS register is set.

Register 17: I²C Slave Raw Interrupt Status (I2CSRIS), offset 0x810


This register specifies whether an interrupt is pending.

I2C Slave Raw Interrupt Status (I2CSRIS)

I2C 0 base: 0x4002.0000 I2C 1 base: 0x4002.1000 I2C 1 base: 0x4002.1000 I2C 2 base: 0x4002.2000 I2C 3 base: 0x4002.3000 I2C 4 base: 0x400C.0000 I2C 5 base: 0x400C.1000

Offset 0x810

Type RO, reset 0x0000.0000



Bit/Field	Name	Туре	Reset	Description
31:3	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
2	STOPRIS	RO	0	Stop Condition Raw Interrupt Status
				Value Description
				0 No interrupt.
				1 A STOP condition interrupt is pending.
				This bit is cleared by writing a 1 to the STOPIC bit in the I2CSICR register.
1	STARTRIS	RO	0	Start Condition Raw Interrupt Status
				Value Description
				0 No interrupt.
				1 A START condition interrupt is pending.
				This bit is cleared by writing a 1 to the STARTIC bit in the I2CSICR register.
0	DATARIS	RO	0	Data Raw Interrupt Status
				Value Description
				0 No interrupt.
				A data assistant or data assistant intermedia a condition

A data received or data requested interrupt is pending.

This bit is cleared by writing a 1 to the DATAIC bit in the I2CSICR register.


Register 18: I²C Slave Masked Interrupt Status (I2CSMIS), offset 0x814

This register specifies whether an interrupt was signaled.

I2C Slave Masked Interrupt Status (I2CSMIS)

I2C 0 base: 0x4002.0000 I2C 1 base: 0x4002.1000 I2C 1 base: 0x4002.1000 I2C 2 base: 0x4002.2000 I2C 3 base: 0x4002.3000 I2C 4 base: 0x400C.0000 I2C 5 base: 0x400C.1000 Offset 0x814

Type RO, reset 0x0000.0000



Bit/Field	Name	Туре	Reset	Description
31:3	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
2	STOPMIS	RO	0	Stop Condition Masked Interrupt Status
				Value Description
				O An interrupt has not occurred or is masked.
				1 An unmasked STOP condition interrupt was signaled is pending.
				This bit is cleared by writing a 1 to the STOPIC bit in the I2CSICR register.
1	STARTMIS	RO	0	Start Condition Masked Interrupt Status
				Value Description
				O An interrupt has not occurred or is masked.
				 An unmasked START condition interrupt was signaled is pending.
				This bit is cleared by writing a 1 to the STARTIC bit in the I2CSICR register.
0	DATAMIS	RO	0	Data Masked Interrupt Status
				Value Description

- 0 An interrupt has not occurred or is masked.
- 1 An unmasked data received or data requested interrupt was signaled is pending.

This bit is cleared by writing a 1 to the <code>DATAIC</code> bit in the <code>I2CSICR</code> register.


Register 19: I²C Slave Interrupt Clear (I2CSICR), offset 0x818

This register clears the raw interrupt. A read of this register returns no meaningful data.

I2C Slave Interrupt Clear (I2CSICR)

I2C 0 base: 0x4002.0000 I2C 1 base: 0x4002.1000 I2C 2 base: 0x4002.2000 I2C 3 base: 0x4002.3000 I2C 4 base: 0x400C.0000 I2C 5 base: 0x400C.1000 Offset 0x818

Type WO, reset 0x0000.0000



Bit/Field	Name	Туре	Reset	Description
31:3	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
2	STOPIC	WO	0	Stop Condition Interrupt Clear
				Writing a 1 to this bit clears the STOPRIS bit in the I2CSRIS register and the STOPMIS bit in the I2CSMIS register.
				A read of this register returns no meaningful data.
1	STARTIC	WO	0	Start Condition Interrupt Clear
				Writing a 1 to this bit clears the STARTRIS bit in the I2CSRIS register and the STARTMIS bit in the I2CSMIS register.
				A read of this register returns no meaningful data.
0	DATAIC	WO	0	Data Interrupt Clear
				Writing a 1 to this bit clears the STOPRIS bit in the I2CSRIS register and the STOPMIS bit in the I2CSMIS register.

A read of this register returns no meaningful data.

Register 20: I²C Slave Own Address 2 (I2CSOAR2), offset 0x81C


This register consists of seven address bits that identify the alternate address for the I^2C device on the I^2C bus.

I2C Slave Own Address 2 (I2CSOAR2)

I2C 0 base: 0x4002.0000 I2C 1 base: 0x4002.1000 I2C 2 base: 0x4002.2000 I2C 3 base: 0x4002.3000 I2C 4 base: 0x400C.0000 I2C 5 base: 0x400C.1000

Offset 0x81C

Type R/W, reset 0x0000.0000



Bit/Field	Name	Туре	Reset	Description
31:8	reserved	RO	0x0000.00	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
7	OAR2EN	R/W	0	I ² C Slave Own Address 2 Enable
				Value Description
				0 The alternate address is disabled.
				1 Enables the use of the alternate address in the OAR2 field.
6:0	OAR2	R/W	0x00	I ² C Slave Own Address 2
				This field specifies the alternate OAR2 address


Register 21: I²C Slave ACK Control (I2CSACKCTL), offset 0x820

This register enables the I²C slave to NACK for invalid data or command or ACK for valid data or command. The I²C clock is pulled low after the last data bit until this register is written.



I2C 0 base: 0x4002.0000 I2C 1 base: 0x4002.1000 I2C 2 base: 0x4002.2000 I2C 3 base: 0x4002.3000 I2C 4 base: 0x400C.0000 I2C 5 base: 0x400C.1000

Offset 0x820 Type R/W, reset 0x0000.0000



Bit/Field	Name	Type	Reset	Description
31:2	reserved	RO	0x0000.000	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
1	ACKOVAL	R/W	0	I ² C Slave ACK Override Value
				Value Description
				0 An ACK is sent indicating valid data or command.
				1 A NACK is sent indicating invalid data or command.
0	ACKOEN	R/W	0	I ² C Slave ACK Override Enable

Value Description

- 0 A response in not provided.
- 1 An ACK or NACK is sent according to the value written to the ACKOVAL bit.

16.8 Register Descriptions (I²C Status and Control)

The remainder of this section lists and describes the I²C status and control registers, in numerical order by address offset.


Register 22: I²C Peripheral Properties (I2CPP), offset 0xFC0

The **I2CPP** register provides information regarding the properties of the I²C module.

I2C Peripheral Properties (I2CPP)

I2C 0 base: 0x4002.0000 I2C 1 base: 0x4002.1000 I2C 2 base: 0x4002.2000 I2C 3 base: 0x4002.3000 I2C 4 base: 0x400C.0000 I2C 5 base: 0x400C.1000 Offset 0xFC0

Type RO, reset 0x0000.0001



Bit/Field	Name	Туре	Reset	Description
31:1	reserved	RO	0x0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
0	HS	RO	0x1	High-Speed Capable

Value Description

- The interface is capable of Standard, Fast, or Fast mode plus operation.
- 1 The interface is capable of High-Speed operation.

Register 23: I²C Peripheral Configuration (I2CPC), offset 0xFC4

The **I2CPC** register allows software to enable features present in the I²C module.

I2C Peripheral Configuration (I2CPC)

0


0

0

I2C 0 base: 0x4002.0000 I2C 1 base: 0x4002.1000 I2C 2 base: 0x4002.2000 I2C 3 base: 0x4002.3000 I2C 4 base: 0x400C.0000 I2C 5 base: 0x400C.1000 Offset 0xFC4 Type RO, reset 0x0000.0001

Reset

0



0

0

0

Bit/Field	Name	Туре	Reset	Description
31:1	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
0	HS	R/W	1	High-Speed Capable

Value Description

0

0

- The interface is set to Standard, Fast or Fast mode plus operation.
- The interface is set to High-Speed operation. Note that this encoding may only be used if the HS bit in the **I2CPP** register is set. Otherwise, this encoding is not available.

0

17 Controller Area Network (CAN) Module


Controller Area Network (CAN) is a multicast, shared serial bus standard for connecting electronic control units (ECUs). CAN was specifically designed to be robust in electromagnetically-noisy environments and can utilize a differential balanced line like RS-485 or a more robust twisted-pair wire. Originally created for automotive purposes, it is also used in many embedded control applications (such as industrial and medical). Bit rates up to 1 Mbps are possible at network lengths less than 40 meters. Decreased bit rates allow longer network distances (for example, 125 Kbps at 500 meters).

The Stellaris® LM4F232H5QC microcontroller includes two CAN units with the following features:

- CAN protocol version 2.0 part A/B
- Bit rates up to 1 Mbps
- 32 message objects with individual identifier masks
- Maskable interrupt
- Disable Automatic Retransmission mode for Time-Triggered CAN (TTCAN) applications
- Programmable loopback mode for self-test operation
- Programmable FIFO mode enables storage of multiple message objects
- Gluelessly attaches to an external CAN transceiver through the CANnTX and CANnRX signals

17.1 Block Diagram

Figure 17-1. CAN Controller Block Diagram



17.2 Signal Description

The following table lists the external signals of the CAN controller and describes the function of each. The CAN controller signals are alternate functions for some GPIO signals and default to be GPIO signals at reset. The column in the table below titled "Pin Mux/Pin Assignment" lists the possible GPIO pin placements for the CAN signals. The AFSEL bit in the **GPIO Alternate Function Select (GPIOAFSEL)** register (page 670) should be set to choose the CAN controller function. The number in parentheses is the encoding that must be programmed into the PMCn field in the **GPIO Port Control (GPIOPCTL)** register (page 688) to assign the CAN signal to the specified GPIO port pin. For more information on configuring GPIOs, see "General-Purpose Input/Outputs (GPIOs)" on page 646.

Table 17-1. Controller Area Network Signals (100LQFP)

Pin Name	Pin Number	Pin Mux / Pin Assignment	Pin Type	Buffer Type ^a	Description
CAN0Rx	40 92 95	PF0 (3) PB4 (8) PE4 (8)	I	TTL	CAN module 0 receive.
CANOTX	43 91 96	PF3 (3) PB5 (8) PE5 (8)	0	TTL	CAN module 0 transmit.
CAN1Rx	26 89	PA0 (8) PE6 (8)	I	TTL	CAN module 1 receive.
CAN1Tx	27 90	PA1 (8) PE7 (8)	0	TTL	CAN module 1 transmit.

a. The TTL designation indicates the pin has TTL-compatible voltage levels.

17.3 Functional Description

The Stellaris CAN controller conforms to the CAN protocol version 2.0 (parts A and B). Message transfers that include data, remote, error, and overload frames with an 11-bit identifier (standard) or a 29-bit identifier (extended) are supported. Transfer rates can be programmed up to 1 Mbps.

The CAN module consists of three major parts:

- CAN protocol controller and message handler
- Message memory
- CAN register interface

A data frame contains data for transmission, whereas a remote frame contains no data and is used to request the transmission of a specific message object. The CAN data/remote frame is constructed as shown in Figure 17-2.




Figure 17-2. CAN Data/Remote Frame

The protocol controller transfers and receives the serial data from the CAN bus and passes the data on to the message handler. The message handler then loads this information into the appropriate message object based on the current filtering and identifiers in the message object memory. The message handler is also responsible for generating interrupts based on events on the CAN bus.

The message object memory is a set of 32 identical memory blocks that hold the current configuration, status, and actual data for each message object. These memory blocks are accessed via either of the CAN message object register interfaces.

The message memory is not directly accessible in the Stellaris memory map, so the Stellaris CAN controller provides an interface to communicate with the message memory via two CAN interface register sets for communicating with the message objects. These two interfaces must be used to read or write to each message object. The two message object interfaces allow parallel access to the CAN controller message objects when multiple objects may have new information that must be processed. In general, one interface is used for transmit data and one for receive data.

17.3.1 Initialization

To use the CAN controller, the peripheral clock must be enabled using the **RCGC0** register (see page 449). In addition, the clock to the appropriate GPIO module must be enabled via the **RCGC2** register (see page 457). To find out which GPIO port to enable, refer to Table 23-4 on page 1358. Set the GPIO AFSEL bits for the appropriate pins (see page 670). Configure the PMCn fields in the **GPIOPCTL** register to assign the CAN signals to the appropriate pins. See page 688 and Table 23-5 on page 1367.

Software initialization is started by setting the INIT bit in the **CAN Control (CANCTL)** register (with software or by a hardware reset) or by going bus-off, which occurs when the transmitter's error counter exceeds a count of 255. While INIT is set, all message transfers to and from the CAN bus are stopped and the CANnTX signal is held High. Entering the initialization state does not change the configuration of the CAN controller, the message objects, or the error counters. However, some configuration registers are only accessible while in the initialization state.

To initialize the CAN controller, set the CAN Bit Timing (CANBIT) register and configure each message object. If a message object is not needed, label it as not valid by clearing the MSGVAL bit in the CAN IFn Arbitration 2 (CANIFnARB2) register. Otherwise, the whole message object must be initialized, as the fields of the message object may not have valid information, causing unexpected results. Both the INIT and CCE bits in the CANCTL register must be set in order to access the CANBIT register and the CAN Baud Rate Prescaler Extension (CANBRPE) register to configure the bit timing. To leave the initialization state, the INIT bit must be cleared. Afterwards, the internal Bit Stream Processor (BSP) synchronizes itself to the data transfer on the CAN bus by waiting for the occurrence of a sequence of 11 consecutive recessive bits (indicating a bus idle condition) before it takes part in bus activities and starts message transfers. Message object initialization does not require the CAN to be in the initialization state and can be done on the fly. However, message objects should all be configured to particular identifiers or set to not valid before message transfer starts. To change the configuration of a message object during normal operation, clear the MSGVAL bit in the CANIFnARB2 register to indicate that the message object is not valid during the change. When the configuration is completed, set the MSGVAL bit again to indicate that the message object is once again valid.

17.3.2 Operation

Two sets of CAN Interface Registers (**CANIF1x** and **CANIF2x**) are used to access the message objects in the Message RAM. The CAN controller coordinates transfers to and from the Message RAM to and from the registers. The two sets are independent and identical and can be used to queue transactions. Generally, one interface is used to transmit data and one is used to receive data.

Once the CAN module is initialized and the INIT bit in the **CANCTL** register is cleared, the CAN module synchronizes itself to the CAN bus and starts the message transfer. As each message is received, it goes through the message handler's filtering process, and if it passes through the filter, is stored in the message object specified by the MNUM bit in the **CAN IFn Command Request** (**CANIFnCRQ**) register. The whole message (including all arbitration bits, data-length code, and eight data bytes) is stored in the message object. If the Identifier Mask (the MSK bits in the **CAN IFn Mask 1** and **CAN IFn Mask 2** (**CANIFnMSKn**) registers) is used, the arbitration bits that are masked to "don't care" may be overwritten in the message object.

The CPU may read or write each message at any time via the CAN Interface Registers. The message handler guarantees data consistency in case of concurrent accesses.

The transmission of message objects is under the control of the software that is managing the CAN hardware. Message objects can be used for one-time data transfers or can be permanent message objects used to respond in a more periodic manner. Permanent message objects have all arbitration and control set up, and only the data bytes are updated. At the start of transmission, the appropriate TXRQST bit in the CAN Transmission Request n (CANTXRQn) register and the NEWDAT bit in the CAN New Data n (CANNWDAn) register are set. If several transmit messages are assigned to the same message object (when the number of message objects is not sufficient), the whole message object has to be configured before the transmission of this message is requested.

The transmission of any number of message objects may be requested at the same time; they are transmitted according to their internal priority, which is based on the message identifier (MNUM) for the message object, with 1 being the highest priority and 32 being the lowest priority. Messages may be updated or set to not valid any time, even when their requested transmission is still pending. The old data is discarded when a message is updated before its pending transmission has started. Depending on the configuration of the message object, the transmission of a message may be requested autonomously by the reception of a remote frame with a matching identifier.

Transmission can be automatically started by the reception of a matching remote frame. To enable this mode, set the RMTEN bit in the CAN IFn Message Control (CANIFnMCTL) register. A matching received remote frame causes the TXRQST bit to be set, and the message object automatically transfers its data or generates an interrupt indicating a remote frame was requested. A remote frame can be strictly a single message identifier, or it can be a range of values specified in the message object. The CAN mask registers, CANIFnMSKn, configure which groups of frames are identified as remote frame requests. The UMASK bit in the CANIFnMCTL register enables the MSK bits in the CANIFnMSKn register to filter which frames are identified as a remote frame request. The MXTD bit in the CANIFnMSK2 register should be set if a remote frame request is expected to be triggered by 29-bit extended identifiers.

17.3.3 Transmitting Message Objects

If the internal transmit shift register of the CAN module is ready for loading, and if a data transfer is not occurring between the CAN Interface Registers and message RAM, the valid message object with the highest priority that has a pending transmission request is loaded into the transmit shift register by the message handler and the transmission is started. The message object's NEWDAT bit in the CANNWDAn register is cleared. After a successful transmission, and if no new data was written to the message object since the start of the transmission, the TXRQST bit in the CANTXRQn register is cleared. If the CAN controller is configured to interrupt on a successful transmission of a message object, (the TXIE bit in the CAN IFn Message Control (CANIFnMCTL) register is set), the INTPND bit in the CANIFnMCTL register is set after a successful transmission. If the CAN module has lost the arbitration or if an error occurred during the transmission, the message is re-transmitted as soon as the CAN bus is free again. If, meanwhile, the transmission of a message with higher priority has been requested, the messages are transmitted in the order of their priority.

17.3.4 Configuring a Transmit Message Object

The following steps illustrate how to configure a transmit message object.

- 1. In the CAN IFn Command Mask (CANIFnCMASK) register:
 - Set the WRNRD bit to specify a write to the **CANIFnCMASK** register; specify whether to transfer the IDMASK, DIR, and MXTD of the message object into the **CAN IFn** registers using the MASK bit
 - Specify whether to transfer the ID, DIR, XTD, and MSGVAL of the message object into the interface registers using the ARB bit
 - Specify whether to transfer the control bits into the interface registers using the CONTROL bit
 - Specify whether to clear the INTPND bit in the CANIFnMCTL register using the CLRINTPND bit
 - Specify whether to clear the NEWDAT bit in the CANNWDAn register using the NEWDAT bit
 - Specify which bits to transfer using the DATAA and DATAB bits
- 2. In the **CANIFnMSK1** register, use the MSK[15:0] bits to specify which of the bits in the 29-bit or 11-bit message identifier are used for acceptance filtering. Note that MSK[15:0] in this register are used for bits [15:0] of the 29-bit message identifier and are not used for an 11-bit identifier. A value of 0x00 enables all messages to pass through the acceptance filtering. Also

- note that in order for these bits to be used for acceptance filtering, they must be enabled by setting the UMASK bit in the **CANIFNMCTL** register.
- 3. In the CANIFnMSK2 register, use the MSK[12:0] bits to specify which of the bits in the 29-bit or 11-bit message identifier are used for acceptance filtering. Note that MSK[12:0] are used for bits [28:16] of the 29-bit message identifier; whereas MSK[12:2] are used for bits [10:0] of the 11-bit message identifier. Use the MXTD and MDIR bits to specify whether to use XTD and DIR for acceptance filtering. A value of 0x00 enables all messages to pass through the acceptance filtering. Also note that in order for these bits to be used for acceptance filtering, they must be enabled by setting the UMASK bit in the CANIFnMCTL register.
- 4. For a 29-bit identifier, configure ID[15:0] in the CANIFnARB1 register for bits [15:0] of the message identifier and ID[12:0] in the CANIFnARB2 register for bits [28:16] of the message identifier. Set the XTD bit to indicate an extended identifier; set the DIR bit to indicate transmit; and set the MSGVAL bit to indicate that the message object is valid.
- 5. For an 11-bit identifier, disregard the **CANIFnARB1** register and configure ID[12:2] in the **CANIFnARB2** register for bits [10:0] of the message identifier. Clear the XTD bit to indicate a standard identifier; set the DIR bit to indicate transmit; and set the MSGVAL bit to indicate that the message object is valid.
- **6.** In the **CANIFnMCTL** register:
 - Optionally set the UMASK bit to enable the mask (MSK, MXTD, and MDIR specified in the CANIFnMSK1 and CANIFnMSK2 registers) for acceptance filtering
 - Optionally set the TXIE bit to enable the INTPND bit to be set after a successful transmission
 - Optionally set the RMTEN bit to enable the TXRQST bit to be set on the reception of a matching remote frame allowing automatic transmission
 - Set the EOB bit for a single message object
 - Configure the DLC[3:0] field to specify the size of the data frame. Take care during this configuration not to set the NEWDAT, MSGLST, INTPND or TXRQST bits.
- 7. Load the data to be transmitted into the CAN IFn Data (CANIFnDA1, CANIFnDA2, CANIFnDB1, CANIFnDB2) registers. Byte 0 of the CAN data frame is stored in DATA [7:0] in the CANIFnDA1 register.
- 8. Program the number of the message object to be transmitted in the MNUM field in the CAN IFn Command Request (CANIFnCRQ) register.
- 9. When everything is properly configured, set the TXRQST bit in the CANIFnMCTL register. Once this bit is set, the message object is available to be transmitted, depending on priority and bus availability. Note that setting the RMTEN bit in the CANIFnMCTL register can also start message transmission if a matching remote frame has been received.

17.3.5 Updating a Transmit Message Object

The CPU may update the data bytes of a Transmit Message Object any time via the CAN Interface Registers and neither the MSGVAL bit in the CANIFnARB2 register nor the TXRQST bits in the CANIFnMCTL register have to be cleared before the update.

Even if only some of the data bytes are to be updated, all four bytes of the corresponding **CANIFnDAn/CANIFnDBn** register have to be valid before the content of that register is transferred to the message object. Either the CPU must write all four bytes into the **CANIFnDAn/CANIFnDBn** register or the message object is transferred to the **CANIFnDAn/CANIFnDBn** register before the CPU writes the new data bytes.

In order to only update the data in a message object, the WRNRD, DATAA and DATAB bits in the **CANIFnMSKn** register are set, followed by writing the updated data into **CANIFnDA1**, **CANIFnDA2**, **CANIFnDB1**, and **CANIFnDB2** registers, and then the number of the message object is written to the MNUM field in the **CAN IFn Command Request (CANIFnCRQ)** register. To begin transmission of the new data as soon as possible, set the TXRQST bit in the **CANIFnMSKn** register.

To prevent the clearing of the TXRQST bit in the **CANIFnMCTL** register at the end of a transmission that may already be in progress while the data is updated, the NEWDAT and TXRQST bits have to be set at the same time in the **CANIFnMCTL** register. When these bits are set at the same time, NEWDAT is cleared as soon as the new transmission has started.

17.3.6 Accepting Received Message Objects

When the arbitration and control field (the ID and XTD bits in the **CANIFnARB2** and the RMTEN and DLC[3:0] bits of the **CANIFnMCTL** register) of an incoming message is completely shifted into the CAN controller, the message handling capability of the controller starts scanning the message RAM for a matching valid message object. To scan the message RAM for a matching message object, the controller uses the acceptance filtering programmed through the mask bits in the **CANIFnMSKn** register and enabled using the UMASK bit in the **CANIFnMCTL** register. Each valid message object, starting with object 1, is compared with the incoming message to locate a matching message object in the message RAM. If a match occurs, the scanning is stopped and the message handler proceeds depending on whether it is a data frame or remote frame that was received.

17.3.7 Receiving a Data Frame

The message handler stores the message from the CAN controller receive shift register into the matching message object in the message RAM. The data bytes, all arbitration bits, and the DLC bits are all stored into the corresponding message object. In this manner, the data bytes are connected with the identifier even if arbitration masks are used. The NEWDAT bit of the CANIFnMCTL register is set to indicate that new data has been received. The CPU should clear this bit when it reads the message object to indicate to the controller that the message has been received, and the buffer is free to receive more messages. If the CAN controller receives a message and the NEWDAT bit is already set, the MSGLST bit in the CANIFnMCTL register is set to indicate that the previous data was lost. If the system requires an interrupt on successful reception of a frame, the RXIE bit of the CANIFnMCTL register should be set. In this case, the INTPND bit of the same register is set, causing the CANINT register to point to the message object that just received a message. The TXRQST bit of this message object should be cleared to prevent the transmission of a remote frame.

17.3.8 Receiving a Remote Frame

A remote frame contains no data, but instead specifies which object should be transmitted. When a remote frame is received, three different configurations of the matching message object have to be considered:

Table 17-2. Message Object Configurations

Configuration in CANIFnMCTL	Description
 DIR = 1 (direction = transmit); programmed in the CANIFnARB2 register RMTEN = 1 (set the TXRQST bit of the CANIFnMCTL register at reception of the frame to enable transmission) UMASK = 1 or 0 	At the reception of a matching remote frame, the TXRQST bit of this message object is set. The rest of the message object remains unchanged, and the controller automatically transfers the data in the message object as soon as possible.
■ DIR = 1 (direction = transmit); programmed in the CANIFnARB2 register ■ RMTEN = 0 (do not change the TXRQST bit of the CANIFnMCTL register at reception of the frame) ■ UMASK = 0 (ignore mask in the CANIFnMSKn register)	At the reception of a matching remote frame, the TXRQST bit of this message object remains unchanged, and the remote frame is ignored. This remote frame is disabled, the data is not transferred and nothing indicates that the remote frame ever happened.
■ DIR = 1 (direction = transmit); programmed in the CANIFnARB2 register ■ RMTEN = 0 (do not change the TXRQST bit of the CANIFnMCTL register at reception of the frame) ■ UMASK = 1 (use mask (MSK, MXTD, and MDIR in the CANIFnMSKn register) for acceptance filtering)	At the reception of a matching remote frame, the TXRQST bit of this message object is cleared. The arbitration and control field (ID + XTD + RMTEN + DLC) from the shift register is stored into the message object in the message RAM, and the NEWDAT bit of this message object is set. The data field of the message object remains unchanged; the remote frame is treated similar to a received data frame. This mode is useful for a remote data request from another CAN device for which the Stellaris controller does not have readily available data. The software must fill the data and answer the frame manually.

17.3.9 Receive/Transmit Priority

The receive/transmit priority for the message objects is controlled by the message number. Message object 1 has the highest priority, while message object 32 has the lowest priority. If more than one transmission request is pending, the message objects are transmitted in order based on the message object with the lowest message number. This prioritization is separate from that of the message identifier which is enforced by the CAN bus. As a result, if message object 1 and message object 2 both have valid messages to be transmitted, message object 1 is always transmitted first regardless of the message identifier in the message object itself.

17.3.10 Configuring a Receive Message Object

The following steps illustrate how to configure a receive message object.

- 1. Program the **CAN IFn Command Mask (CANIFnCMASK)** register as described in the "Configuring a Transmit Message Object" on page 1058 section, except that the WRNRD bit is set to specify a write to the message RAM.
- 2. Program the CANIFnMSK1 and CANIFnMSK2 registers as described in the "Configuring a Transmit Message Object" on page 1058 section to configure which bits are used for acceptance filtering. Note that in order for these bits to be used for acceptance filtering, they must be enabled by setting the UMASK bit in the CANIFnMCTL register.
- 3. In the CANIFnMSK2 register, use the MSK[12:0] bits to specify which of the bits in the 29-bit or 11-bit message identifier are used for acceptance filtering. Note that MSK[12:0] are used for bits [28:16] of the 29-bit message identifier; whereas MSK[12:2] are used for bits [10:0] of the 11-bit message identifier. Use the MXTD and MDIR bits to specify whether to use XTD and

DIR for acceptance filtering. A value of 0x00 enables all messages to pass through the acceptance filtering. Also note that in order for these bits to be used for acceptance filtering, they must be enabled by setting the UMASK bit in the **CANIFNMCTL** register.

- 4. Program the CANIFNARB1 and CANIFNARB2 registers as described in the "Configuring a Transmit Message Object" on page 1058 section to program XTD and ID bits for the message identifier to be received; set the MSGVAL bit to indicate a valid message; and clear the DIR bit to specify receive.
- **5.** In the **CANIFnMCTL** register:
 - Optionally set the UMASK bit to enable the mask (MSK, MXTD, and MDIR specified in the CANIFnMSK1 and CANIFnMSK2 registers) for acceptance filtering
 - Optionally set the RXIE bit to enable the INTPND bit to be set after a successful reception
 - Clear the RMTEN bit to leave the TXRQST bit unchanged
 - Set the EOB bit for a single message object
 - Configure the DLC[3:0] field to specify the size of the data frame

Take care during this configuration not to set the NEWDAT, MSGLST, INTPND or TXRQST bits.

6. Program the number of the message object to be received in the MNUM field in the **CAN IFn Command Request (CANIFnCRQ)** register. Reception of the message object begins as soon as a matching frame is available on the CAN bus.

When the message handler stores a data frame in the message object, it stores the received Data Length Code and eight data bytes in the **CANIFnDA1**, **CANIFnDA2**, **CANIFnDB1**, and **CANIFnDB2** register. Byte 0 of the CAN data frame is stored in DATA[7:0] in the **CANIFnDA1** register. If the Data Length Code is less than 8, the remaining bytes of the message object are overwritten by unspecified values.

The CAN mask registers can be used to allow groups of data frames to be received by a message object. The CAN mask registers, **CANIFnMSKn**, configure which groups of frames are received by a message object. The UMASK bit in the **CANIFnMCTL** register enables the MSK bits in the **CANIFnMSKn** register to filter which frames are received. The MXTD bit in the **CANIFnMSK2** register should be set if only 29-bit extended identifiers are expected by this message object.

17.3.11 Handling of Received Message Objects

The CPU may read a received message any time via the CAN Interface registers because the data consistency is guaranteed by the message handler state machine.

Typically, the CPU first writes 0x007F to the **CANIFnCMSK** register and then writes the number of the message object to the **CANIFnCRQ** register. That combination transfers the whole received message from the message RAM into the Message Buffer registers (**CANIFnMSKn**, **CANIFnARBn**, and **CANIFnMCTL**). Additionally, the NEWDAT and INTPND bits are cleared in the message RAM, acknowledging that the message has been read and clearing the pending interrupt generated by this message object.

If the message object uses masks for acceptance filtering, the **CANIFnARBn** registers show the full, unmasked ID for the received message.

The NEWDAT bit in the **CANIFnMCTL** register shows whether a new message has been received since the last time this message object was read. The MSGLST bit in the **CANIFnMCTL** register shows whether more than one message has been received since the last time this message object was read. MSGLST is not automatically cleared, and should be cleared by software after reading its status.

Using a remote frame, the CPU may request new data from another CAN node on the CAN bus. Setting the TXRQST bit of a receive object causes the transmission of a remote frame with the receive object's identifier. This remote frame triggers the other CAN node to start the transmission of the matching data frame. If the matching data frame is received before the remote frame could be transmitted, the TXRQST bit is automatically reset. This prevents the possible loss of data when the other device on the CAN bus has already transmitted the data slightly earlier than expected.

17.3.11.1 Configuration of a FIFO Buffer

With the exception of the EOB bit in the **CANIFnMCTL** register, the configuration of receive message objects belonging to a FIFO buffer is the same as the configuration of a single receive message object (see "Configuring a Receive Message Object" on page 1061). To concatenate two or more message objects into a FIFO buffer, the identifiers and masks (if used) of these message objects have to be programmed to matching values. Due to the implicit priority of the message objects, the message object with the lowest message object number is the first message object in a FIFO buffer. The EOB bit of all message objects of a FIFO buffer except the last one must be cleared. The EOB bit of the last message object of a FIFO buffer is set, indicating it is the last entry in the buffer.

17.3.11.2 Reception of Messages with FIFO Buffers

Received messages with identifiers matching to a FIFO buffer are stored starting with the message object with the lowest message number. When a message is stored into a message object of a FIFO buffer, the NEWDAT of the **CANIFNMCTL** register bit of this message object is set. By setting NEWDAT while EOB is clear, the message object is locked and cannot be written to by the message handler until the CPU has cleared the NEWDAT bit. Messages are stored into a FIFO buffer until the last message object of this FIFO buffer is reached. Until all of the preceding message objects have been released by clearing the NEWDAT bit, all further messages for this FIFO buffer are written into the last message object of the FIFO buffer and therefore overwrite previous messages.

17.3.11.3 Reading from a FIFO Buffer

When the CPU transfers the contents of a message object from a FIFO buffer by writing its number to the CANIFnCRQ register, the TXRQST and CLRINTPND bits in the CANIFnCMSK register should be set such that the NEWDAT and INTPEND bits in the CANIFnMCTL register are cleared after the read. The values of these bits in the CANIFnMCTL register always reflect the status of the message object before the bits are cleared. To assure the correct function of a FIFO buffer, the CPU should read out the message objects starting with the message object with the lowest message number. When reading from the FIFO buffer, the user should be aware that a new received message is placed in the message object with the lowest message number for which the NEWDAT bit of the CANIFnMCTL register is clear. As a result, the order of the received messages in the FIFO is not guaranteed. Figure 17-3 on page 1064 shows how a set of message objects which are concatenated to a FIFO Buffer can be handled by the CPU.




Figure 17-3. Message Objects in a FIFO Buffer

17.3.12 Handling of Interrupts

If several interrupts are pending, the **CAN Interrupt (CANINT)** register points to the pending interrupt with the highest priority, disregarding their chronological order. The status interrupt has the highest

priority. Among the message interrupts, the message object's interrupt with the lowest message number has the highest priority. A message interrupt is cleared by clearing the message object's INTPND bit in the **CANIFNMCTL** register or by reading the **CAN Status (CANSTS)** register. The status Interrupt is cleared by reading the **CANSTS** register.

The interrupt identifier INTID in the **CANINT** register indicates the cause of the interrupt. When no interrupt is pending, the register reads as 0x0000. If the value of the INTID field is different from 0, then an interrupt is pending. If the IE bit is set in the **CANCTL** register, the interrupt line to the interrupt controller is active. The interrupt line remains active until the INTID field is 0, meaning that all interrupt sources have been cleared (the cause of the interrupt is reset), or until IE is cleared, which disables interrupts from the CAN controller.

The INTID field of the **CANINT** register points to the pending message interrupt with the highest interrupt priority. The SIE bit in the **CANCTL** register controls whether a change of the RXOK, TXOK, and LEC bits in the **CANSTS** register can cause an interrupt. The EIE bit in the **CANCTL**register controls whether a change of the BOFF and EWARN bits in the **CANSTS** register can cause an interrupt. The IE bit in the **CANCTL** register controls whether any interrupt from the CAN controller actually generates an interrupt to the interrupt controller. The **CANINT** register is updated even when the IE bit in the **CANCTL** register is clear, but the interrupt is not indicated to the CPU.

A value of 0x8000 in the **CANINT** register indicates that an interrupt is pending because the CAN module has updated, but not necessarily changed, the **CANSTS** register, indicating that either an error or status interrupt has been generated. A write access to the **CANSTS** register can clear the RXOK, TXOK, and LEC bits in that same register; however, the only way to clear the source of a status interrupt is to read the **CANSTS** register.

The source of an interrupt can be determined in two ways during interrupt handling. The first is to read the INTID bit in the **CANINT** register to determine the highest priority interrupt that is pending, and the second is to read the **CAN Message Interrupt Pending (CANMSGnINT)** register to see all of the message objects that have pending interrupts.

An interrupt service routine reading the message that is the source of the interrupt may read the message and clear the message object's INTPND bit at the same time by setting the CLRINTPND bit in the **CANIFTCMSK** register. Once the INTPND bit has been cleared, the **CANINT** register contains the message number for the next message object with a pending interrupt.

17.3.13 Test Mode

A Test Mode is provided which allows various diagnostics to be performed. Test Mode is entered by setting the <code>TEST</code> bit in the <code>CANCTL</code> register. Once in Test Mode, the <code>TX[1:0]</code>, <code>LBACK</code>, <code>SILENT</code> and <code>BASIC</code> bits in the <code>CAN Test</code> (<code>CANTST</code>) register can be used to put the <code>CAN</code> controller into the various diagnostic modes. The <code>RX</code> bit in the <code>CANTST</code> register allows monitoring of the <code>CANNRX</code> signal. All <code>CANTST</code> register functions are disabled when the <code>TEST</code> bit is cleared.

17.3.13.1 Silent Mode

Silent Mode can be used to analyze the traffic on a CAN bus without affecting it by the transmission of dominant bits (Acknowledge Bits, Error Frames). The CAN Controller is put in Silent Mode setting the SILENT bit in the **CANTST** register. In Silent Mode, the CAN controller is able to receive valid data frames and valid remote frames, but it sends only recessive bits on the CAN bus and cannot start a transmission. If the CAN Controller is required to send a dominant bit (ACK bit, overload flag, or active error flag), the bit is rerouted internally so that the CAN Controller monitors this dominant bit, although the CAN bus remains in recessive state.

17.3.13.2 Loopback Mode

Loopback mode is useful for self-test functions. In Loopback Mode, the CAN Controller internally routes the CANnTX signal on to the CANnRX signal and treats its own transmitted messages as received messages and stores them (if they pass acceptance filtering) into the message buffer. The CAN Controller is put in Loopback Mode by setting the LBACK bit in the **CANTST** register. To be independent from external stimulation, the CAN Controller ignores acknowledge errors (a recessive bit sampled in the acknowledge slot of a data/remote frame) in Loopback Mode. The actual value of the CANNRX signal is disregarded by the CAN Controller. The transmitted messages can be monitored on the CANNTX signal.

17.3.13.3 Loopback Combined with Silent Mode

Loopback Mode and Silent Mode can be combined to allow the CAN Controller to be tested without affecting a running CAN system connected to the CANnTX and CANnRX signals. In this mode, the CANnRX signal is disconnected from the CAN Controller and the CANnTX signal is held recessive. This mode is enabled by setting both the LBACK and SILENT bits in the **CANTST** register.

17.3.13.4 Basic Mode

Basic Mode allows the CAN Controller to be operated without the Message RAM. In Basic Mode, The CANIF1 registers are used as the transmit buffer. The transmission of the contents of the IF1 registers is requested by setting the BUSY bit of the **CANIF1CRQ** register. The CANIF1 registers are locked while the BUSY bit is set. The BUSY bit indicates that a transmission is pending. As soon the CAN bus is idle, the CANIF1 registers are loaded into the shift register of the CAN Controller and transmission is started. When the transmission has completed, the BUSY bit is cleared and the locked CANIF1 registers are released. A pending transmission can be aborted at any time by clearing the BUSY bit in the **CANIF1CRQ** register while the CANIF1 registers are locked. If the CPU has cleared the BUSY bit, a possible retransmission in case of lost arbitration or an error is disabled.

The CANIF2 Registers are used as a receive buffer. After the reception of a message, the contents of the shift register are stored in the CANIF2 registers, without any acceptance filtering. Additionally, the actual contents of the shift register can be monitored during the message transfer. Each time a read message object is initiated by setting the BUSY bit of the **CANIF2CRQ** register, the contents of the shift register are stored into the CANIF2 registers.

In Basic Mode, all message-object-related control and status bits and of the control bits of the **CANIFnCMSK** registers are not evaluated. The message number of the **CANIFnCRQ** registers is also not evaluated. In the **CANIF2MCTL** register, the NEWDAT and MSGLST bits retain their function, the DLC[3:0] field shows the received DLC, the other control bits are cleared.

Basic Mode is enabled by setting the BASIC bit in the CANTST register.

17.3.13.5 Transmit Control

Software can directly override control of the CANnTX signal in four different ways.

- CANnTX is controlled by the CAN Controller
- The sample point is driven on the CANnTX signal to monitor the bit timing
- CANnTX drives a low value
- CANnTX drives a high value

The last two functions, combined with the readable CAN receive pin CANnRX, can be used to check the physical layer of the CAN bus.

The Transmit Control function is enabled by programming the $\mathtt{TX[1:0]}$ field in the **CANTST** register. The three test functions for the CANnTX signal interfere with all CAN protocol functions. $\mathtt{TX[1:0]}$ must be cleared when CAN message transfer or Loopback Mode, Silent Mode, or Basic Mode are selected.

17.3.14 Bit Timing Configuration Error Considerations

Even if minor errors in the configuration of the CAN bit timing do not result in immediate failure, the performance of a CAN network can be reduced significantly. In many cases, the CAN bit synchronization amends a faulty configuration of the CAN bit timing to such a degree that only occasionally an error frame is generated. In the case of arbitration, however, when two or more CAN nodes simultaneously try to transmit a frame, a misplaced sample point may cause one of the transmitters to become error passive. The analysis of such sporadic errors requires a detailed knowledge of the CAN bit synchronization inside a CAN node and of the CAN nodes' interaction on the CAN bus.

17.3.15 Bit Time and Bit Rate

The CAN system supports bit rates in the range of lower than 1 Kbps up to 1000 Kbps. Each member of the CAN network has its own clock generator. The timing parameter of the bit time can be configured individually for each CAN node, creating a common bit rate even though the CAN nodes' oscillator periods may be different.

Because of small variations in frequency caused by changes in temperature or voltage and by deteriorating components, these oscillators are not absolutely stable. As long as the variations remain inside a specific oscillator's tolerance range, the CAN nodes are able to compensate for the different bit rates by periodically resynchronizing to the bit stream.

According to the CAN specification, the bit time is divided into four segments (see Figure 17-4 on page 1068): the Synchronization Segment, the Propagation Time Segment, the Phase Buffer Segment 1, and the Phase Buffer Segment 2. Each segment consists of a specific, programmable number of time quanta (see Table 17-3 on page 1068). The length of the time quantum (t_q), which is the basic time unit of the bit time, is defined by the CAN controller's input clock ($f_{\rm SYS}$) and the Baud Rate Prescaler (BRP):

$$t_q = BRP / fsys$$

The fsys input clock is the system clock frequency as configured by the **RCC** or **RCC2** registers (see page 255 or page 263).

The Synchronization Segment Sync is that part of the bit time where edges of the CAN bus level are expected to occur; the distance between an edge that occurs outside of Sync and the Sync is called the phase error of that edge.

The Propagation Time Segment Prop is intended to compensate for the physical delay times within the CAN network.

The Phase Buffer Segments Phase1 and Phase2 surround the Sample Point.

The (Re-)Synchronization Jump Width (SJW) defines how far a resynchronization may move the Sample Point inside the limits defined by the Phase Buffer Segments to compensate for edge phase errors.

A given bit rate may be met by different bit-time configurations, but for the proper function of the CAN network, the physical delay times and the oscillator's tolerance range have to be considered.

Figure 17-4. CAN Bit Time




Table 17-3. CAN Protocol Ranges^a

Parameter	Range	Remark
BRP	[1 64]	Defines the length of the time quantum $t_{\rm q}$. The CANBRPE register can be used to extend the range to 1024.
Sync	1 t _q	Fixed length, synchronization of bus input to system clock
Prop	[1 8] t _q	Compensates for the physical delay times
Phase1	[1 8] t _q	May be lengthened temporarily by synchronization
Phase2	[1 8] t _q	May be shortened temporarily by synchronization
SJW	[1 4] t _q	May not be longer than either Phase Buffer Segment

a. This table describes the minimum programmable ranges required by the CAN protocol.

The bit timing configuration is programmed in two register bytes in the **CANBIT** register. In the **CANBIT** register, the four components TSEG2, TSEG1, SJW, and BRP have to be programmed to a numerical value that is one less than its functional value; so instead of values in the range of [1..n], values in the range of [0..n-1] are programmed. That way, for example, SJW (functional range of [1..4]) is represented by only two bits in the SJW bit field. Table 17-4 shows the relationship between the **CANBIT** register values and the parameters.

Table 17-4. CANBIT Register Values

CANBIT Register Field	Setting
TSEG2	Phase2 - 1
TSEG1	Prop + Phase1 - 1
SJW	SJW - 1
BRP	BRP

Therefore, the length of the bit time is (programmed values):

[TSEG1 + TSEG2 + 3]
$$\times$$
 t_q or (functional values):
 [Sync + Prop + Phase1 + Phase2] \times t_q

The data in the **CANBIT** register is the configuration input of the CAN protocol controller. The baud rate prescaler (configured by the BRP field) defines the length of the time quantum, the basic time

unit of the bit time; the bit timing logic (configured by TSEG1, TSEG2, and SJW) defines the number of time quanta in the bit time.

The processing of the bit time, the calculation of the position of the sample point, and occasional synchronizations are controlled by the CAN controller and are evaluated once per time quantum.

The CAN controller translates messages to and from frames. In addition, the controller generates and discards the enclosing fixed format bits, inserts and extracts stuff bits, calculates and checks the CRC code, performs the error management, and decides which type of synchronization is to be used. The bit value is received or transmitted at the sample point. The information processing time (IPT) is the time after the sample point needed to calculate the next bit to be transmitted on the CAN bus. The IPT includes any of the following: retrieving the next data bit, handling a CRC bit, determining if bit stuffing is required, generating an error flag or simply going idle.

The IPT is application-specific but may not be longer than 2 t_q ; the CAN's IPT is 0 t_q . Its length is the lower limit of the programmed length of Phase2. In case of synchronization, Phase2 may be shortened to a value less than IPT, which does not affect bus timing.

17.3.16 Calculating the Bit Timing Parameters

Usually, the calculation of the bit timing configuration starts with a required bit rate or bit time. The resulting bit time (1/bit rate) must be an integer multiple of the system clock period.

The bit time may consist of 4 to 25 time quanta. Several combinations may lead to the required bit time, allowing iterations of the following steps.

The first part of the bit time to be defined is Prop. Its length depends on the delay times measured in the system. A maximum bus length as well as a maximum node delay has to be defined for expandable CAN bus systems. The resulting time for Prop is converted into time quanta (rounded up to the nearest integer multiple of t_{α}).

Sync is 1 t_q long (fixed), which leaves (bit time - Prop - 1) t_q for the two Phase Buffer Segments. If the number of remaining t_q is even, the Phase Buffer Segments have the same length, that is, Phase2 = Phase1, else Phase2 = Phase1 + 1.

The minimum nominal length of Phase2 has to be regarded as well. Phase2 may not be shorter than the CAN controller's Information Processing Time, which is, depending on the actual implementation, in the range of $[0..2] t_a$.

The length of the synchronization jump width is set to the least of 4, Phase1 or Phase2.

The oscillator tolerance range necessary for the resulting configuration is calculated by the formula given below:

$$(1 - df) \times fnom \leq fosc \leq (1 + df) \times fnom$$

where:

- df = Maximum tolerance of oscillator frequency
- fosc = Actual oscillator frequency
- fnom = Nominal oscillator frequency

Maximum frequency tolerance must take into account the following formulas:

$$df \le \frac{(Phase_seg1, Phase_seg2) \min}{2 \times (13 \times tbit - Phase_Seg2)}$$

$$df \max = 2 \times df \times fnom$$

where:

- Phase1 and Phase2 are from Table 17-3 on page 1068
- tbit = Bit Time
- dfmax = Maximum difference between two oscillators

If more than one configuration is possible, that configuration allowing the highest oscillator tolerance range should be chosen.

CAN nodes with different system clocks require different configurations to come to the same bit rate. The calculation of the propagation time in the CAN network, based on the nodes with the longest delay times, is done once for the whole network.

The CAN system's oscillator tolerance range is limited by the node with the lowest tolerance range.

The calculation may show that bus length or bit rate have to be decreased or that the oscillator frequencies' stability has to be increased in order to find a protocol-compliant configuration of the CAN bit timing.

17.3.16.1 Example for Bit Timing at High Baud Rate

In this example, the frequency of CAN clock is 25 MHz, and the bit rate is 1 Mbps.

```
bit time = 1 \mus = n * t<sub>q</sub> = 5 * t<sub>q</sub>
t_{\alpha} = 200 \text{ ns}
t_q = (Baud rate Prescaler)/CAN Clock
Baud rate Prescaler = t_q * CAN Clock
Baud rate Prescaler = 200E-9 * 25E6 = 5
tSync = 1 * t_q = 200 ns
                                          \\fixed at 1 time quanta
delay of bus driver 50 ns
delay of receiver circuit 30 ns
delay of bus line (40m) 220 ns
tProp 400 ns = 2 * t_{\alpha}
                                           \ is next integer multiple of t_{\alpha}
bit time = tSync + tTSeg1 + tTSeg2 = 5 * t_q
bit time = tSync + tProp + tPhase 1 + tPhase2
tPhase 1 + tPhase2 = bit time - tSync - tProp
tPhase 1 + tPhase 2 = (5 * t_q) - (1 * t_q) - (2 * t_q)
tPhase 1 + tPhase2 = 2 * t_{\alpha}
tPhase1 = 1 * t_{a}
tPhase2 = 1 * t_g
                                          \\tPhase2 = tPhase1
```

In the above example, the bit field values for the **CANBIT** register are:

TSEG2	= TSeg2 -1
	= 1-1
	= 0
TSEG1	= TSeg1 -1
	= 3-1
	= 2
SJW	= SJW -1
	= 1-1
	= 0
BRP	= Baud rate prescaler - 1
	= 5-1
	=4

The final value programmed into the **CANBIT** register = 0x0204.

17.3.16.2 Example for Bit Timing at Low Baud Rate

In this example, the frequency of the CAN clock is 50 MHz, and the bit rate is 100 Kbps.

```
bit time = 10 \mus = n * t<sub>q</sub> = 10 * t<sub>q</sub>
t_q = 1 \mu s
t<sub>q</sub> = (Baud rate Prescaler)/CAN Clock
Baud rate Prescaler = t_q * CAN Clock
Baud rate Prescaler = 1E-6 * 50E6 = 50
tSync = 1 * t_q = 1 \mu s
                                          \\fixed at 1 time quanta
delay of bus driver 200 ns
delay of receiver circuit 80 ns
delay of bus line (40m) 220 ns
tProp 1 \mu s = 1 * t_q
                                         \label{eq:lambda} \ is next integer multiple of t_{q}
bit time = tSync + tTSeg1 + tTSeg2 = 10 * t_q
bit time = tSync + tProp + tPhase 1 + tPhase2
tPhase 1 + tPhase2 = bit time - tSync - tProp
tPhase 1 + tPhase 2 = (10 * t_q) - (1 * t_q) - (1 * t_q)
tPhase 1 + tPhase2 = 8 * t_{\alpha}
tPhase1 = 4 * t_q
tPhase2 = 4 * t_{g}
                                         \\tPhase1 = tPhase2
```

TSEG2	= TSeg2 -1
	= 4-1
	= 3
TSEG1	= TSeg1 -1
	= 5-1
	= 4
SJW	= SJW -1
	= 4-1
	= 3
BRP	= Baud rate prescaler - 1
	= 50-1
	=49

The final value programmed into the **CANBIT** register = 0x34F1.

17.4 Register Map

Table 17-5 on page 1072 lists the registers. All addresses given are relative to the CAN base address of:

CAN0: 0x4004.0000CAN1: 0x4004.1000

Note that the CAN controller clock must be enabled before the registers can be programmed (see page 342). There must be a delay of 3 system clocks after the CAN module clock is enabled before any CAN module registers are accessed.

Table 17-5. CAN Register Map

Offset	Name	Туре	Reset	Description	See page
0x000	CANCTL	R/W	0x0000.0001	CAN Control	1075
0x004	CANSTS	R/W	0x0000.0000	CAN Status	1077
0x008	CANERR	RO	0x0000.0000	CAN Error Counter	1080
0x00C	CANBIT	R/W	0x0000.2301	CAN Bit Timing	1081
0x010	CANINT	RO	0x0000.0000	CAN Interrupt	1082
0x014	CANTST	R/W	0x0000.0000	CAN Test	1083
0x018	CANBRPE	R/W	0x0000.0000	CAN Baud Rate Prescaler Extension	1085
0x020	CANIF1CRQ	R/W	0x0000.0001	CAN IF1 Command Request	1086

Table 17-5. CAN Register Map (continued)

Offset	Name	Туре	Reset	Description	See page
0x024	CANIF1CMSK	R/W	0x0000.0000	CAN IF1 Command Mask	1087
0x028	CANIF1MSK1	R/W	0x0000.FFFF	CAN IF1 Mask 1	1090
0x02C	CANIF1MSK2	R/W	0x0000.FFFF	CAN IF1 Mask 2	1091
0x030	CANIF1ARB1	R/W	0x0000.0000	CAN IF1 Arbitration 1	1093
0x034	CANIF1ARB2	R/W	0x0000.0000	CAN IF1 Arbitration 2	1094
0x038	CANIF1MCTL	R/W	0x0000.0000	CAN IF1 Message Control	1096
0x03C	CANIF1DA1	R/W	0x0000.0000	CAN IF1 Data A1	1099
0x040	CANIF1DA2	R/W	0x0000.0000	CAN IF1 Data A2	1099
0x044	CANIF1DB1	R/W	0x0000.0000	CAN IF1 Data B1	1099
0x048	CANIF1DB2	R/W	0x0000.0000	CAN IF1 Data B2	1099
0x080	CANIF2CRQ	R/W	0x0000.0001	CAN IF2 Command Request	1086
0x084	CANIF2CMSK	R/W	0x0000.0000	CAN IF2 Command Mask	1087
0x088	CANIF2MSK1	R/W	0x0000.FFFF	CAN IF2 Mask 1	1090
0x08C	CANIF2MSK2	R/W	0x0000.FFFF	CAN IF2 Mask 2	1091
0x090	CANIF2ARB1	R/W	0x0000.0000	CAN IF2 Arbitration 1	1093
0x094	CANIF2ARB2	R/W	0x0000.0000	CAN IF2 Arbitration 2	1094
0x098	CANIF2MCTL	R/W	0x0000.0000	CAN IF2 Message Control	1096
0x09C	CANIF2DA1	R/W	0x0000.0000	CAN IF2 Data A1	1099
0x0A0	CANIF2DA2	R/W	0x0000.0000	CAN IF2 Data A2	1099
0x0A4	CANIF2DB1	R/W	0x0000.0000	CAN IF2 Data B1	1099
0x0A8	CANIF2DB2	R/W	0x0000.0000	CAN IF2 Data B2	1099
0x100	CANTXRQ1	RO	0x0000.0000	CAN Transmission Request 1	1100
0x104	CANTXRQ2	RO	0x0000.0000	CAN Transmission Request 2	1100
0x120	CANNWDA1	RO	0x0000.0000	CAN New Data 1	1101
0x124	CANNWDA2	RO	0x0000.0000	CAN New Data 2	1101
0x140	CANMSG1INT	RO	0x0000.0000	CAN Message 1 Interrupt Pending	1102
0x144	CANMSG2INT	RO	0x0000.0000	CAN Message 2 Interrupt Pending	1102
0x160	CANMSG1VAL	RO	0x0000.0000	CAN Message 1 Valid	1103
0x164	CANMSG2VAL	RO	0x0000.0000	CAN Message 2 Valid	1103

17.5 CAN Register Descriptions

The remainder of this section lists and describes the CAN registers, in numerical order by address offset. There are two sets of Interface Registers that are used to access the Message Objects in

the Message RAM: ${\bf CANIF1x}$ and ${\bf CANIF2x}$. The function of the two sets are identical and are used to queue transactions.

Register 1: CAN Control (CANCTL), offset 0x000

This control register initializes the module and enables test mode and interrupts.

The bus-off recovery sequence (see CAN Specification Rev. 2.0) cannot be shortened by setting or clearing INIT. If the device goes bus-off, it sets INIT, stopping all bus activities. Once INIT has been cleared by the CPU, the device then waits for 129 occurrences of Bus Idle (129 * 11 consecutive High bits) before resuming normal operations. At the end of the bus-off recovery sequence, the Error Management Counters are reset.


During the waiting time after INIT is cleared, each time a sequence of 11 High bits has been monitored, a BITERROR0 code is written to the **CANSTS** register (the LEC field = 0x5), enabling the CPU to readily check whether the CAN bus is stuck Low or continuously disturbed, and to monitor the proceeding of the bus-off recovery sequence.

CAN Control (CANCTL)

CAN0 base: 0x4004.0000 CAN1 base: 0x4004.1000

Offset 0x000

Type R/W, reset 0x0000.0001



Bit/Field	Name	Туре	Reset	Description						
31:8	reserved	RO	0x0000.00	compatibil	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.					
7	TEST	R/W	0	Test Mode	Enable					
				Value	Description					
				0	The CAN controller is operating normally.					
				1	The CAN controller is in test mode.					
6	CCE	R/W	0	Configurat	ion Change Enable					
				Value	Description					
				0	Write accesses to the CANBIT register are not allowed.					
				1	Write accesses to the CANBIT register are allowed if the INIT bit is 1.					
5	DAR	R/W	0	Disable Au	utomatic-Retransmission					
				Value	Description					
				0	Auto-retransmission of disturbed messages is enabled.					
				1	Auto-retransmission is disabled.					

Bit/Field	Name	Туре	Reset	Descripti	Description				
4	reserved	RO	0	compatib	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.				
3	EIE	R/W	0	Error Inte	errupt Enable				
				Value	Description				
				0	No error status interrupt is generated.				
				1	A change in the BOFF or EWARN bits in the CANSTS register generates an interrupt.				
2	SIE	R/W	0	Status In	nterrupt Enable				
				Value	Description				
				0	No status interrupt is generated.				
				1	An interrupt is generated when a message has successfully been transmitted or received, or a CAN bus error has been detected. A change in the TXOK, RXOK or LEC bits in the CANSTS register generates an interrupt.				
1	IE	R/W	0	CAN Inte	errupt Enable				
				Value	Description				
				0	Interrupts disabled.				
				1	Interrupts enabled.				
0	INIT	R/W	1	Initializat	tion				
				Value	Description				
				0	Normal operation.				
				1	Initialization started.				

Register 2: CAN Status (CANSTS), offset 0x004

Important: This register is read-sensitive. See the register description for details.

The status register contains information for interrupt servicing such as Bus-Off, error count threshold, and error types.

The LEC field holds the code that indicates the type of the last error to occur on the CAN bus. This field is cleared when a message has been transferred (reception or transmission) without error. The unused error code 0x7 may be written by the CPU to manually set this field to an invalid error so that it can be checked for a change later.

An error interrupt is generated by the BOFF and EWARN bits, and a status interrupt is generated by the RXOK, TXOK, and LEC bits, if the corresponding enable bits in the **CAN Control (CANCTL)** register are set. A change of the EPASS bit or a write to the RXOK, TXOK, or LEC bits does not generate an interrupt.


Reading the **CAN Status (CANSTS)** register clears the **CAN Interrupt (CANINT)** register, if it is pending.

CAN Status (CANSTS)

CAN0 base: 0x4004.0000 CAN1 base: 0x4004.1000

Offset 0x004

Type R/W, reset 0x0000.0000



Bit/Field	Name	Type	Reset	Description	n					
2.0. 10.0		.,,,,	. 10001	2000p						
31:8	reserved	RO	0x0000.00	compatibili	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.					
7	BOFF	RO	0	Bus-Off Status						
				Value	Description					
				0	The CAN controller is not in bus-off state.					
				1	The CAN controller is in bus-off state.					
6	EWARN	RO	0	Warning S	tatus					
				Value	Description					
				0	Both error counters are below the error warning limit of 96.					
				1	At least one of the error counters has reached the error warning limit of 96.					

Bit/Field	Name	Туре	Reset	Descripti	on				
5	EPASS	RO	0	Error Passive					
				Value	Description				
				0	The CAN module is in the Error Active state, that is, the receive or transmit error count is less than or equal to 127.				
				1	The CAN module is in the Error Passive state, that is, the receive or transmit error count is greater than 127.				
4	RXOK	R/W	0	Received	d a Message Successfully				
				Value	Description				
				0	Since this bit was last cleared, no message has been successfully received.				
				1	Since this bit was last cleared, a message has been successfully received, independent of the result of the acceptance filtering.				
				This bit n	nust be cleared by writing a 0 to it.				
3	TXOK	R/W	0	Transmit	ted a Message Successfully				
				Value	Description				
				0	Since this bit was last cleared, no message has been successfully transmitted.				
				1	Since this bit was last cleared, a message has been successfully transmitted error-free and acknowledged by at least one other node.				

This bit must be cleared by writing a 0 to it.

Bit/Field	Name	Typo	Reset	Doscript	ion				
DIVI ICIU	Name	Туре	Neset	Description					
2:0	LEC	R/W	0x0	Last Error Code					
				This is t	he type of the last error to occur on the CAN bus.				
				Value	Description				
				0x0	No Error				
				0x1	Stuff Error				
					More than 5 equal bits in a sequence have occurred in a part of a received message where this is not allowed.				
				0x2	Format Error				
					A fixed format part of the received frame has the wrong format.				
				0x3	ACK Error				
					The message transmitted was not acknowledged by another node.				
				0x4	Bit 1 Error				
					When a message is transmitted, the CAN controller monitors the data lines to detect any conflicts. When the arbitration field is transmitted, data conflicts are a part of the arbitration protocol. When other frame fields are transmitted, data conflicts are considered errors.				
					A Bit 1 Error indicates that the device wanted to send a High level (logical 1) but the monitored bus value was Low (logical 0).				
				0x5	Bit 0 Error				
					A Bit 0 Error indicates that the device wanted to send a Low level (logical 0), but the monitored bus value was High (logical 1).				
					During bus-off recovery, this status is set each time a sequence of 11 High bits has been monitored. By checking for this status, software can monitor the proceeding of the bus-off recovery sequence without any disturbances to the bus.				
				0x6	CRC Error				
					The CRC checksum was incorrect in the received message, indicating that the calculated value received did not match the calculated CRC of the data.				
				0x7	No Event				
					When the LEC bit shows this value, no CAN bus event was detected since this value was written to the LEC field.				

Register 3: CAN Error Counter (CANERR), offset 0x008

This register contains the error counter values, which can be used to analyze the cause of an error.

CAN Error Counter (CANERR)

CAN0 base: 0x4004.0000 CAN1 base: 0x4004.1000 Offset 0x008

Type RO, reset 0x0000.0000

	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16	
		1	1				1	rese	rved	1	1	1					
Type	RO 0	RO	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO	RO 0	RO 0	RO	RO	
Reset	U	0	U	U	U	U	U	U	U	U	U	0	U	U	0	0	
	15	14	13	12	11	10	9	8	7	6	5	4	3	2	1	0	
	RP		•	_	REC		•			•	•	. TE	EC	•	•	<u> </u>	
Type Reset	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	
Reset	U	U	U	U	U	U	U	U	U	U	U	U	U	U	U	U	
_	Bit/Field		Name Type Reset Description														
	olul lelu		ivaii	IC	1) }) C	Neset	Des	Cription								
	31:16		reserv	ved	R)	0x0000			ould not							
											with future products, the value of a reserved bit should be cross a read-modify-write operation.						
								pres	oci veu a	C1033 a 1	cau-mo	any-write	operatio)II.			
	15		RP)	R)	0	Rec	eived Er	ror Pass	ive						
								Valu	Value Description								
								0	The Receive Error counter is below the Error level (127 or less).					Error Pa	ssive		
								The Receive Error counter has reached the level (128 or greater).						ne Error	Passive		
	14:8		RE	С	RO)	0x00	Rec	eive Err	or Count	er						
								This	field co	ntains th	e state o	of the rec	eiver err	or count	er (0 to	127).	
	7:0		TEC	2	RO)	0x00	Trar	nsmit Err	or Count	ter						

This field contains the state of the transmit error counter (0 to 255).

Register 4: CAN Bit Timing (CANBIT), offset 0x00C

This register is used to program the bit width and bit quantum. Values are programmed to the system clock frequency. This register is write-enabled by setting the CCE and INIT bits in the **CANCTL** register. See "Bit Time and Bit Rate" on page 1067 for more information.

CAN Bit Timing (CANBIT)

CAN0 base: 0x4004.0000 CAN1 base: 0x4004.1000

Offset 0x00C


Bit/Field

Name

Type

Reset

Type R/W, reset 0x0000.2301



Description

31:15	reserved	RO	0x0000	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
14:12	TSEG2	R/W	0x2	Time Segment after Sample Point 0x00-0x07: The actual interpretation by the hardware of this value is such that one more than the value programmed here is used.
				So, for example, the reset value of 0x2 means that 3 (2+1) bit time quanta are defined for Phase2 (see Figure 17-4 on page 1068). The bit time quanta is defined by the BRP field.
11:8	TSEG1	R/W	0x3	Time Segment Before Sample Point
				0x00-0x0F: The actual interpretation by the hardware of this value is such that one more than the value programmed here is used.
				So, for example, the reset value of 0x3 means that 4 (3+1) bit time quanta are defined for <code>Phasel</code> (see Figure 17-4 on page 1068). The bit time quanta is defined by the <code>BRP</code> field.
7:6	SJW	R/W	0x0	(Re)Synchronization Jump Width
				0x00-0x03: The actual interpretation by the hardware of this value is such that one more than the value programmed here is used.
				During the start of frame (SOF), if the CAN controller detects a phase error (misalignment), it can adjust the length of ${ t TSEG2}$ or ${ t TSEG1}$ by the value in ${ t SJW}$. So the reset value of 0 adjusts the length by 1 bit time quanta.
5:0	BRP	R/W	0x1	Baud Rate Prescaler
				The value by which the oscillator frequency is divided for generating the bit time quanta. The bit time is built up from a multiple of this quantum.

0x00-0x03F: The actual interpretation by the hardware of this value is such that one more than the value programmed here is used. $\tt BRP$ defines the number of CAN clock periods that make up 1 bit time

The **CANBRPE** register can be used to further divide the bit time.

quanta, so the reset value is 2 bit time quanta (1+1).

Register 5: CAN Interrupt (CANINT), offset 0x010

This register indicates the source of the interrupt.

If several interrupts are pending, the **CAN Interrupt (CANINT)** register points to the pending interrupt with the highest priority, disregarding the order in which the interrupts occurred. An interrupt remains pending until the CPU has cleared it. If the <code>INTID</code> field is not 0x0000 (the default) and the <code>IE</code> bit in the **CANCTL** register is set, the interrupt is active. The interrupt line remains active until the <code>INTID</code> field is cleared by reading the **CANSTS** register, or until the <code>IE</code> bit in the **CANCTL** register is cleared.


Note: Reading the **CAN Status (CANSTS)** register clears the **CAN Interrupt (CANINT)** register, if it is pending.

CAN Interrupt (CANINT)

CAN0 base: 0x4004.0000 CAN1 base: 0x4004.1000

Offset 0x010

Type RO, reset 0x0000.0000



Bit/Field	Name	Type	Reset	Description
31:16	reserved	RO	0x0000	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
15:0	INTID	RO	0x0000	Interrupt Identifier

Value

The number in this field indicates the source of the interrupt.

0x0000No interrupt pending0x0001-0x0020Number of the message object that caused the interrupt0x0021-0x7FFFReserved0x8000Status Interrupt

Description

0x8001-0xFFFF Reserved


Register 6: CAN Test (CANTST), offset 0x014

This register is used for self-test and external pin access. It is write-enabled by setting the TEST bit in the CANCTL register. Different test functions may be combined, however, CAN transfers are affected if the TX bits in this register are not zero.

CAN Test (CANTST)

CAN0 base: 0x4004.0000 CAN1 base: 0x4004.1000 Offset 0x014

Type R/W, reset 0x0000.0000



Bit/Field	Name	Type	Reset	Description				
31:8	reserved	RO	0x0000.00	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.				
7	RX	RO	0	Receive Obs	servation			
				Value	Description			
				0	The CANnRx pin is low.			
				1	The CANnRx pin is high.			
6:5	TX	R/W	0x0	Transmit Cor	ntrol			
				Overrides co	ontrol of the CANnTx pin.			

Value	Description
0x0	CAN Module Control
	${\tt CANnTx}$ is controlled by the CAN module; default operation
0x1	Sample Point
	The sample point is driven on the ${\tt CANnTx}$ signal. This mode is useful to monitor bit timing.
0x2	Driven Low
	CANnTx drives a low value. This mode is useful for checking the physical layer of the CAN bus.
0x3	Driven High
	CANnTx drives a high value. This mode is useful for

checking the physical layer of the CAN bus.

Bit/Field	Name	Туре	Reset	Description	Description			
4	LBACK	R/W	0	Loopback	Mode			
				Value	Description			
				0	Loopback mode is disabled.			
				1	Loopback mode is enabled. In loopback mode, the data from the transmitter is routed into the receiver. Any data on the receive input is ignored.			
3	SILENT	R/W	0	Silent Mod	de			
				Value	Description			
				0	Silent mode is disabled.			
				1	Silent mode is enabled. In silent mode, the CAN controller does not transmit data but instead monitors the bus. This mode is also known as Bus Monitor mode.			
2	BASIC	R/W	0	Basic Mod	le			
				Value	Description			
				0	Basic mode is disabled.			
				1	Basic mode is enabled. In basic mode, software should use the CANIF1 registers as the transmit buffer and use the CANIF2 registers as the receive buffer.			
1:0	reserved	RO	0x0	compatibil	should not rely on the value of a reserved bit. To provide ity with future products, the value of a reserved bit should be across a read-modify-write operation.			

Register 7: CAN Baud Rate Prescaler Extension (CANBRPE), offset 0x018


This register is used to further divide the bit time set with the BRP bit in the CANBIT register. It is write-enabled by setting the CCE bit in the **CANCTL** register.

CAN Baud Rate Prescaler Extension (CANBRPE)

CAN0 base: 0x4004.0000 CAN1 base: 0x4004.1000

Offset 0x018

Type R/W, reset 0x0000.0000



Bit/Field	Name	Type	Reset	Description
31:4	reserved	RO	0x0000.000	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
3:0	BRPE	R/W	0x0	Baud Rate Prescaler Extension

0x00-0x0F: Extend the BRP bit in the CANBIT register to values up to 1023. The actual interpretation by the hardware is one more than the value programmed by BRPE (MSBs) and BRP (LSBs).

Register 8: CAN IF1 Command Request (CANIF1CRQ), offset 0x020 Register 9: CAN IF2 Command Request (CANIF2CRQ), offset 0x080

A message transfer is started as soon as there is a write of the message object number to the MNUM field when the TXRQST bit in the **CANIF1MCTL** register is set. With this write operation, the BUSY bit is automatically set to indicate that a transfer between the CAN Interface Registers and the internal message RAM is in progress. After a wait time of 3 to 6 CAN_CLK periods, the transfer between the interface register and the message RAM completes, which then clears the BUSY bit.

CAN IFn Command Request (CANIFnCRQ)

CAN0 base: 0x4004.0000 CAN1 base: 0x4004.1000 Offset 0x020

Type R/W, reset 0x0000.0001

	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16
				1				rese	rved I							
Туре	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO
Reset	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0
	15	14	13	12	11	10	9	8	7	6	5	4	3	2	1	0
	BUSY			1		reserved		1	1				MN	UM		
Туре	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	R/W	R/W	R/W	R/W	R/W	R/W
Reset	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	1

Bit/Field	Name	Type	Reset	Description		
31:16	reserved	RO	0x0000	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.		
15	BUSY	RO	0	Busy Flag		
				Value	Description	
				0	This bit is cleared when read/write action has finished.	
				1	This bit is set when a write occurs to the message number in this register.	
14:6	reserved	RO	0x00	compatibility	ould not rely on the value of a reserved bit. To provide with future products, the value of a reserved bit should be cross a read-modify-write operation.	
5:0	MNUM	R/W	0x01	Message Nu	umber	
					of the 32 message objects in the message RAM for data e message objects are numbered from 1 to 32.	
				Value	Description	
				0x00	Reserved	
					0 is not a valid message number; it is interpreted as 0x20, or object 32.	
				0x01-0x20	Message Number	
					Indicates specified message object 1 to 32.	
				0x21-0x3F	Reserved	
					Not a valid message number; values are shifted and it is interpreted as 0x01-0x1F.	

Register 10: CAN IF1 Command Mask (CANIF1CMSK), offset 0x024 Register 11: CAN IF2 Command Mask (CANIF2CMSK), offset 0x084

Reading the Command Mask registers provides status for various functions. Writing to the Command Mask registers specifies the transfer direction and selects which buffer registers are the source or target of the data transfer.

Note that when a read from the message object buffer occurs when the \mathtt{WRNRD} bit is clear and the $\mathtt{CLRINTPND}$ and/or \mathtt{NEWDAT} bits are set, the interrupt pending and/or new data flags in the message object buffer are cleared.

CAN IFn Command Mask (CANIFnCMSK)

CAN0 base: 0x4004.0000 CAN1 base: 0x4004.1000

Offset 0x024

Type R/W, reset 0x0000.0000

Type	K/VV, Tese	et uxuuuu	.0000													
	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16
				•			1	rese	rved	•	'				•	'
Type Reset	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0
	15	14	13	12	11	10	9	8	7	6	5	4	3	2	1	0
	l				erved	r	1 1		WRNRD	MASK	ARB	CONTROL		NEWDAT / TXRQST	DATAA	DATAB
Type Reset	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	R/W 0	R/W 0	R/W 0	R/W 0	R/W 0	R/W 0	R/W 0	R/W 0
E	31:8		Nan reser		Ty R		Reset 0x0000.00	Soft	patibility	with fut	ure prod	the value lucts, the dify-write	value of	a reser		
	7		WRN	RD	R/	W	0	Write	e, Not R	ead						
								Valu	ue D	escriptio	n					
								0	th		тим field	in the CA I in the C A				
								1	n	nessage	object s	in the CA pecified I est (CAN	by the мN	∪M field		
								Note	bı	ıffer can	be clea	and new red by rea PND and/	ading fror	n the bu	uffer (WR1	
	6		MAS	SK	R/	W	0	Acce	ess Mas	k Bits						
								Valu	ne	Desc	ription					
								0		Mask	bits un	changed	=			
								1				IASK + DI face regis		of the	message	e object

Bit/Field	Name	Туре	Reset	Descrip	otion
5	ARB	R/W	0	Access	Arbitration Bits
				Value	Description
				0	Arbitration bits unchanged.
				1	Transfer ID + DIR + XTD + MSGVAL of the message object into the Interface registers.
4	CONTROL	R/W	0	Access	Control Bits
				Value	Description
				0	Control bits unchanged.
				1	Transfer control bits from the CANIFnMCTL register into the Interface registers.
3	CLRINTPND	R/W	0	Clear Ir	nterrupt Pending Bit
				The fun	nction of this bit depends on the configuration of the WRNRD bit.
				Value	Description
				0	If WRNRD is clear, the interrupt pending status is transferred from the message buffer into the CANIFNMCTL register.
					If \mathtt{WRNRD} is set, the \mathtt{INTPND} bit in the message object remains unchanged.
				1	If WRNRD is clear, the interrupt pending status is cleared in the message buffer. Note the value of this bit that is transferred to the CANIFnMCTL register always reflects the status of the bits before clearing.
					If \mathtt{WRNRD} is set, the \mathtt{INTPND} bit is cleared in the message object.
2	NEWDAT / TXRQST	R/W	0	NEWD	AT / TXRQST Bit
_			· ·		nction of this bit depends on the configuration of the WRNRD bit.
				Value	Description
				0	If WRNRD is clear, the value of the new data status is transferred from the message buffer into the CANIFNMCTL register.
					If wrnnr is set, a transmission is not requested.
				1	If WRNRD is clear, the new data status is cleared in the message buffer. Note the value of this bit that is transferred to the CANIFnMCTL register always reflects the status of the bits before clearing

before clearing.

ignored.

If wrnrd is set, a transmission is requested. Note that when this bit is set, the <code>TXRQST</code> bit in the <code>CANIFnMCTL</code> register is

the configuration of the WRNRD bit.
changed.
fer data bytes 0-3 in CANIFnDA1 e message object.
er data bytes 0-3 in message object ANIFnDA2.
n the configuration of the WRNRD bit
changed.
fer data bytes 4-7 in CANIFnDA1 e message object.
er data bytes 4-7 in message object ANIFnDA2.


Register 12: CAN IF1 Mask 1 (CANIF1MSK1), offset 0x028 Register 13: CAN IF2 Mask 1 (CANIF2MSK1), offset 0x088

The mask information provided in this register accompanies the data (CANIFnDAn), arbitration information (CANIFnARBn), and control information (CANIFnMCTL) to the message object in the message RAM. The mask is used with the ID bit in the CANIFnARBn register for acceptance filtering. Additional mask information is contained in the CANIFnMSK2 register.

CAN IFn Mask 1 (CANIFnMSK1)

CAN0 base: 0x4004.0000 CAN1 base: 0x4004.1000 Offset 0x028

Type R/W, reset 0x0000.FFFF



Bit/Field	Name	Туре	Reset	Description
31:16	reserved	RO	0x0000	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
15:0	MSK	R/W	0xFFFF	Identifier Mask

When using a 29-bit identifier, these bits are used for bits [15:0] of the ID. The ${\tt MSK}$ field in the **CANIFnMSK2** register are used for bits [28:16] of the ID. When using an 11-bit identifier, these bits are ignored.

Value	Description
0	The corresponding identifier field (${\tt ID}$) in the message object cannot inhibit the match in acceptance filtering.
1	The corresponding identifier field (ID) is used for acceptance filtering.

Register 14: CAN IF1 Mask 2 (CANIF1MSK2), offset 0x02C Register 15: CAN IF2 Mask 2 (CANIF2MSK2), offset 0x08C

This register holds extended mask information that accompanies the **CANIFnMSK1** register.

CAN IFn Mask 2 (CANIFnMSK2)

CAN0 base: 0x4004.0000 CAN1 base: 0x4004.1000 Offset 0x02C Type R/W, reset 0x0000.FFFF

Type	R/W, res	et 0x0000).FFFF													
	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16
			' '			•	' '	rese	rved	•	•	'		'		
Type Reset	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0
	15	14	13	12	11	10	9	8	7	6	5	4	3	2	1	0
	MXTD	MDIR	reserved			1				MSK	1	1			ı	1
Type Reset	R/W 1	R/W 1	RO 1	R/W 0	R/W 0	R/W 0	R/W 0	R/W 0	R/W 1	R/W 1	R/W 1	R/W 1	R/W 1	R/W 1	R/W 1	R/W 1
E	Bit/Field		Name Type				Reset	Description								
	31:16		reserv	ed .	R	0	0x0000	OO Software should not rely on the value or compatibility with future products, the value of preserved across a read-modify-write of the companion of the compa				value of a reserved bit should be				
15 MXTD R/W				W	1	Mas	sk Exten	ded Iden	tifier							
								Valı	ue	Descrip	tion					
								0		The extended identifier bit (XTD in the CANIFnARB2 register) has no effect on the acceptance filtering.						
								1		The ext filtering		dentifier l	bit XTD is	s used fo	r accep	tance
	14		MDI	R	R/	W	1	Mas	sk Messa	age Direc	ction					
								Vali	ue	Descrip	otion					
								0		The message direction bit (DIR in the CANIFnARB2 register) has no effect for acceptance filtering.						
							1		The message direction bit ${\tt DIR}$ is used for acceptance filtering.							
	13		reserv	ed .	R	0	1	Software should not rely on the value of a reserved compatibility with future products, the value of a reserved across a read-modify-write operation.						a reserv		


Bit/Field	Name	Туре	Reset	Description	n
12:0	MSK	R/W	0xFF	ID. The MS	g a 29-bit identifier, these bits are used for bits [28:16] of the BK field in the CANIFnMSK1 register are used for bits [15:0] When using an 11-bit identifier, MSK[12:2] are used for bits

Register 16: CAN IF1 Arbitration 1 (CANIF1ARB1), offset 0x030 Register 17: CAN IF2 Arbitration 1 (CANIF2ARB1), offset 0x090

These registers hold the identifiers for acceptance filtering.

CAN IFn Arbitration 1 (CANIFnARB1)

CAN0 base: 0x4004.0000 CAN1 base: 0x4004.1000 Offset 0x030 Type R/W, reset 0x0000.0000



Bit/Field	Name	Type	Reset	Description
31:16	reserved	RO	0x0000	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
15:0	ID	R/W	0x0000	Message Identifier

This bit field is used with the ID field in the **CANIFnARB2** register to create the message identifier.

When using a 29-bit identifier, bits 15:0 of the **CANIFnARB1** register are [15:0] of the ID, while bits 12:0 of the **CANIFnARB2** register are [28:16] of the ID.

When using an 11-bit identifier, these bits are not used.

Register 18: CAN IF1 Arbitration 2 (CANIF1ARB2), offset 0x034 Register 19: CAN IF2 Arbitration 2 (CANIF2ARB2), offset 0x094

These registers hold information for acceptance filtering.

CAN IFn Arbitration 2 (CANIFnARB2)

CAN0 base: 0x4004.0000 CAN1 base: 0x4004.1000 Offset 0x034 Type R/W, reset 0x0000.0000

	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16
	'							rese	rved							
Туре	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO
Reset	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0
	15	14	13	12	11	10	9	8	7	6	5	4	3	2	1	0
	MSGVAL	XTD	DIR		1				1	ID			ı			
Type	R/W	R/W	R/W	R/W	R/W	R/W	R/W	R/W	R/W	R/W	R/W	R/W	R/W	R/W	R/W	R/W
Reset	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0

Bit/Field	Name	Type	Reset	Description
31:16	reserved	RO	0x0000	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
15	MSGVAL	R/W	0	Message Valid

Value	Description
0	The message object is ignored by the message handler.
1	The message object is configured and ready to be considered by the message handler within the CAN controller.

All unused message objects should have this bit cleared during initialization and before clearing the INIT bit in the CANCTL register. The MSGVAL bit must also be cleared before any of the following bits are modified or if the message object is no longer required: the ID fields in the CANIFnARBn registers, the XTD and DIR bits in the CANIFnARB2 register, or the DLC field in the CANIFNMCTL register.

14	XTD	R/W	0	Extended Identifie
----	-----	-----	---	--------------------

Value	Description
0	An 11-bit Standard Identifier is used for this message object.
1	A 29-bit Extended Identifier is used for this message object.

Bit/Field	Name	Туре	Reset	Description
13	DIR	R/W	0	Message Direction
				Value Description
				Receive. When the TXRQST bit in the CANIFnMCTL register is set, a remote frame with the identifier of this message object is received. On reception of a data frame with matching identifier, that message is stored in this message object.
				Transmit. When the TXRQST bit in the CANIFNMCTL register is set, the respective message object is transmitted as a data frame. On reception of a remote frame with matching identifier, the TXRQST bit of this message object is set (if RMTEN=1).
12:0	ID	R/W	0x000	Message Identifier
				This bit field is used with the ID field in the CANIFnARB2 register to create the message identifier.
				When using a 29-bit identifier, ID[15:0] of the CANIFnARB1 register are [15:0] of the ID, while these bits, ID[12:0], are [28:16] of the ID.
				When using an 11-bit identifier, $ID[12:2]$ are used for bits [10:0] of the ID. The ID field in the CANIFNARB1 register is ignored.

Register 20: CAN IF1 Message Control (CANIF1MCTL), offset 0x038 Register 21: CAN IF2 Message Control (CANIF2MCTL), offset 0x098

This register holds the control information associated with the message object to be sent to the Message RAM.

CAN IFn Message Control (CANIFnMCTL)

CAN0 base: 0x4004.0000 CAN1 base: 0x4004.1000

Offset 0x038
Type R/W, reset 0x0000.0000

туре	R/W, res	et 0x0000	.0000														
	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16	
				'			'	rese	rved	•	' '		' '	'		•	
Type Reset	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	
	15	14	13	12	11	10	9	8	7	6	5	4	3	2	1	0	
	NEWDAT	MSGLST	INTPND	UMASK	TXIE	RXIE	RMTEN	TXRQST	EOB		reserved			DI	LC	1	
Type Reset	R/W 0	R/W 0	R/W 0	R/W 0	R/W 0	R/W 0	R/W 0	R/W 0	R/W 0	RO 0	RO 0	RO 0	R/W 0	R/W 0	R/W 0	R/W 0	
E	Bit/Field Name Type Reset		Des	cription	1												
	31:16		reserv	ved	R	0	0x0000	Software shou compatibility w preserved acro		ty with fut	ure produ	icts, the	value of	a reserv	•		
	15		NEW	DAT	R/	W	0	0 New Data									
								Valu	ıe	Descripti	on						
						0		No new data has been written into the data portion of th message object by the message handler since the last ti this flag was cleared by the CPU.									
								1			sage hand portion of				en new d	lata into	
	14	MSGLST R/W 0 Message Lost															
								Valu	ıe	Descrip	tion						
								0		No message was lost since the last time this bit was cleared by the CPU.						as	
								1		The message handler stored a new message into this object when NEWDAT was set; the CPU has lost a message.							
										it is only valid for message objects FnARB2 register is clear (receive).				n the DII	R bit in t	ne	
	13		INTP	ND	R/	W	0	Inter	rupt Pe	ending							
								Valu	ıe	Descripti	ion						
								0		This mes	ssage obj	ect is no	ot the sou	urce of a	n interru	pt.	
								1		interrupt	ssage object if priority.	in the C	ANINT r	egister p	oints to	this	

Bit/Field	Name	Туре	Reset	Descript	ion
12	UMASK	R/W	0	Use Acc	eptance Mask
				Value	Description
				0	Mask is ignored.
				1	Use mask (MSK, MXTD, and MDIR bits in the CANIFnMSKn registers) for acceptance filtering.
11	TXIE	R/W	0	Transmi	t Interrupt Enable
				Value	Description
				0	The INTPND bit in the CANIFnMCTL register is unchanged after a successful transmission of a frame.
				1	The INTPND bit in the CANIFNMCTL register is set after a successful transmission of a frame.
10	RXIE	R/W	0	Receive	Interrupt Enable
				Value	Description
				0	The INTPND bit in the CANIFnMCTL register is unchanged after a successful reception of a frame.
				1	The INTPND bit in the CANIFNMCTL register is set after a successful reception of a frame.
9	RMTEN	R/W	0	Remote	Enable
				Value	Description
				0	At the reception of a remote frame, the TXRQST bit in the CANIFnMCTL register is left unchanged.
				1	At the reception of a remote frame, the TXRQST bit in the CANIFnMCTL register is set.
8	TXRQST	R/W	0	Transmit	t Request
				Value	Description
				0	This message object is not waiting for transmission.
				1	The transmission of this message object is requested and is not yet done.
				Note:	If the \mathtt{WRNRD} and \mathtt{TXRQST} bits in the <code>CANIFnCMSK</code> register are set, this bit is ignored.

Bit/Field	Name	Туре	Reset	Description	
7	EOB	R/W	0	End of Buffe	er
				Value	Description
				0	Message object belongs to a FIFO Buffer and is not the last message object of that FIFO Buffer.
				1	Single message object or last message object of a FIFO Buffer.
				to build a FI	sed to concatenate two or more message objects (up to 32) FO buffer. For a single message object (thus not belonging uffer), this bit must be set.
6:4	reserved	RO	0x0	compatibility	ould not rely on the value of a reserved bit. To provide y with future products, the value of a reserved bit should be cross a read-modify-write operation.
3:0	DLC	R/W	0x0	Data Length	n Code
				Value	Description
				0x0-0x8	Specifies the number of bytes in the data frame.
				0x9-0xF	Defaults to a data frame with 8 bytes.
				The DLC fie	ld in the CANIFnMCTL register of a message object must

be defined the same as in all the corresponding objects with the same identifier at other nodes. When the message handler stores a data frame, it writes DLC to the value given by the received message.

Register 22: CAN IF1 Data A1 (CANIF1DA1), offset 0x03C

Register 23: CAN IF1 Data A2 (CANIF1DA2), offset 0x040

Register 24: CAN IF1 Data B1 (CANIF1DB1), offset 0x044

Register 25: CAN IF1 Data B2 (CANIF1DB2), offset 0x048

Register 26: CAN IF2 Data A1 (CANIF2DA1), offset 0x09C

Register 27: CAN IF2 Data A2 (CANIF2DA2), offset 0x0A0

Register 28: CAN IF2 Data B1 (CANIF2DB1), offset 0x0A4

Register 29: CAN IF2 Data B2 (CANIF2DB2), offset 0x0A8


These registers contain the data to be sent or that has been received. In a CAN data frame, data byte 0 is the first byte to be transmitted or received and data byte 7 is the last byte to be transmitted or received. In CAN's serial bit stream, the MSB of each byte is transmitted first.

CAN IFn Data nn (CANIFnDnn)

CAN0 base: 0x4004.0000 CAN1 base: 0x4004.1000

Offset 0x03C

Type R/W, reset 0x0000.0000



Bit/Field	Name	Type	Reset	Description
31:16	reserved	RO	0x0000	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
15:0	DATA	R/W	0x0000	Data

The **CANIFnDA1** registers contain data bytes 1 and 0; **CANIFnDA2** data bytes 3 and 2; **CANIFnDB1** data bytes 5 and 4; and **CANIFnDB2** data bytes 7 and 6.


Register 30: CAN Transmission Request 1 (CANTXRQ1), offset 0x100 Register 31: CAN Transmission Request 2 (CANTXRQ2), offset 0x104

The **CANTXRQ1** and **CANTXRQ2** registers hold the TXRQST bits of the 32 message objects. By reading out these bits, the CPU can check which message object has a transmission request pending. The TXRQST bit of a specific message object can be changed by three sources: (1) the CPU via the **CANIFNMCTL** register, (2) the message handler state machine after the reception of a remote frame, or (3) the message handler state machine after a successful transmission.

The **CANTXRQ1** register contains the TXRQST bits of the first 16 message objects in the message RAM; the **CANTXRQ2** register contains the TXROST bits of the second 16 message objects.

CAN Transmission Request n (CANTXRQn)

CAN0 base: 0x4004.0000 CAN1 base: 0x4004.1000 Offset 0x100 Type RO, reset 0x0000.0000



Bit/Field	name	туре	Reset	Description
31:16	reserved	RO	0x0000	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
15:0	TXRQST	RO	0x0000	Transmission Request Bits

Value	Description
0	The corresponding message object is not waiting for transmission.
1	The transmission of the corresponding message object is requested and is not yet done.

Register 32: CAN New Data 1 (CANNWDA1), offset 0x120 Register 33: CAN New Data 2 (CANNWDA2), offset 0x124

The **CANNWDA1** and **CANNWDA2** registers hold the NEWDAT bits of the 32 message objects. By reading these bits, the CPU can check which message object has its data portion updated. The NEWDAT bit of a specific message object can be changed by three sources: (1) the CPU via the **CANIFnMCTL** register, (2) the message handler state machine after the reception of a data frame, or (3) the message handler state machine after a successful transmission.

The **CANNWDA1** register contains the NEWDAT bits of the first 16 message objects in the message RAM; the **CANNWDA2** register contains the NEWDAT bits of the second 16 message objects.

CAN New Data n (CANNWDAn)

CAN0 base: 0x4004.0000 CAN1 base: 0x4004.1000 Offset 0x120

Type RO, reset 0x0000.0000

	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16
			1	1				rese	rved I							
Туре	RO	RO	RO	RO	RO	RO	RO	RO	RO							
Reset	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0
	15	14	13	12	11	10	9	8	7	6	5	4	3	2	1	0
			1	1	ı			NEW	I I VDAT I			1				
Type	RO	RO	RO	RO	RO	RO	RO	RO	RO							
Reset	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0

Bit/Field	Name	Type	Reset	Description
31:16	reserved	RO	0x0000	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
15:0	NEWDAT	RO	0x0000	New Data Bits

Value	Description
0	No new data has been written into the data portion of the corresponding message object by the message handler since the last time this flag was cleared by the CPU.

The message handler or the CPU has written new data into the data portion of the corresponding message object.

Register 34: CAN Message 1 Interrupt Pending (CANMSG1INT), offset 0x140 Register 35: CAN Message 2 Interrupt Pending (CANMSG2INT), offset 0x144

The **CANMSG1INT** and **CANMSG2INT** registers hold the INTPND bits of the 32 message objects. By reading these bits, the CPU can check which message object has an interrupt pending. The INTPND bit of a specific message object can be changed through two sources: (1) the CPU via the **CANIFNMCTL** register, or (2) the message handler state machine after the reception or transmission of a frame.

This field is also encoded in the **CANINT** register.

The **CANMSG1INT** register contains the INTPND bits of the first 16 message objects in the message RAM; the **CANMSG2INT** register contains the INTPND bits of the second 16 message objects.

CAN Message n Interrupt Pending (CANMSGnINT)

CAN0 base: 0x4004.0000 CAN1 base: 0x4004.1000

Offset 0x140

Type RO, reset 0x0000.0000

	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16
								rese	rved I							
Туре	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO
Reset	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0
	15	14	13	12	11	10	9	8	7	6	5	4	3	2	1	0
			ı		i .			INTI	PND I	ı						
Туре	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO
Reset	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0

Bit/Field	Name	туре	Reset	Description
31:16	reserved	RO	0x0000	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
15:0	INTPND	RO	0x0000	Interrupt Pending Bits

Value	Description
0	The corresponding message object is not the source of an interrupt.
1	The corresponding message object is the source of an

interrupt.

Register 36: CAN Message 1 Valid (CANMSG1VAL), offset 0x160 Register 37: CAN Message 2 Valid (CANMSG2VAL), offset 0x164


The **CANMSG1VAL** and **CANMSG2VAL** registers hold the MSGVAL bits of the 32 message objects. By reading these bits, the CPU can check which message object is valid. The message valid bit of a specific message object can be changed with the **CANIFnARB2** register.

The **CANMSG1VAL** register contains the MSGVAL bits of the first 16 message objects in the message RAM; the **CANMSG2VAL** register contains the MSGVAL bits of the second 16 message objects in the message RAM.

CAN Message n Valid (CANMSGnVAL)

CAN0 base: 0x4004.0000 CAN1 base: 0x4004.1000 Offset 0x160

Type RO, reset 0x0000.0000



Bit/Field	Name	Type	Reset	Description
31:16	reserved	RO	0x0000	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
15:0	MSGVAL	RO	0x0000	Message Valid Bits

\/alue

Description

value	Decompliant
0	The corresponding message object is not configured and is ignored by the message handler.
1	The corresponding message object is configured and should be considered by the message handler

18 Universal Serial Bus (USB) Controller


The Stellaris[®] USB controller operates as a full-speed or low-speed function controller during point-to-point communications with USB Host, Device, or OTG functions. The controller complies with the USB 2.0 standard, which includes SUSPEND and RESUME signaling. 16 endpoints including two hard-wired for control transfers (one endpoint for IN and one endpoint for OUT) plus 14 endpoints defined by firmware along with a dynamic sizable FIFO support multiple packet queueing. µDMA access to the FIFO allows minimal interference from system software. Software-controlled connect and disconnect allows flexibility during USB device start-up. The controller complies with OTG Standard's Session Request Protocol (SRP) and Host Negotiation Protocol (HNP).

The Stellaris USB module has the following features:

- Complies with USB-IF (Implementer's Forum) certification standards
- USB 2.0 full-speed (12 Mbps) and low-speed (1.5 Mbps) operation with integrated PHY
- Link Power Management support which uses link-state awareness to reduce power usage
- 4 transfer types: Control, Interrupt, Bulk, and Isochronous
- 16 endpoints
 - 1 dedicated control IN endpoint and 1 dedicated control OUT endpoint
 - 7 configurable IN endpoints and 7 configurable OUT endpoints
- 4 KB dedicated endpoint memory: one endpoint may be defined for double-buffered 1023-byte isochronous packet size
- VBUS droop and valid ID detection and interrupt
- Efficient transfers using Micro Direct Memory Access Controller (µDMA)
 - Separate channels for transmit and receive for up to three IN endpoints and three OUT endpoints
 - Channel requests asserted when FIFO contains required amount of data

18.1 Block Diagram

Figure 18-1. USB Module Block Diagram



18.2 Signal Description

The following table lists the external signals of the USB controller and describes the function of each. Some USB controller signals are alternate functions for some GPIO signals and default to be GPIO signals at reset. The column in the table below titled "Pin Mux/Pin Assignment" lists the possible GPIO pin placements for these USB signals. The AFSEL bit in the GPIO Alternate Function Select (GPIOAFSEL) register (page 670) should be set to choose the USB function. The number in parentheses is the encoding that must be programmed into the PMCn field in the GPIO Port Control (GPIOPCTL) register (page 688) to assign the USB signal to the specified GPIO port pin. The USBOVBUS and USBOID signals are configured by clearing the appropriate DEN bit in the GPIO Digital Enable (GPIODEN) register. For more information on configuring GPIOs, see "General-Purpose Input/Outputs (GPIOs)" on page 646. The remaining signals (with the word "fixed" in the Pin Mux/Pin Assignment column) have a fixed pin assignment and function.

Note: When used in OTG mode, USBOVBUS and USBOID do not require any configuration as they are dedicated pins for the USB controller and directly connect to the USB connector's VBUS and ID signals. If the USB controller is used as either a dedicated Host or Device, the DEVMODOTG and DEVMOD bits in the USB General-Purpose Control and Status (USBGPCS) register can be used to connect the USBOVBUS and USBOID inputs to fixed levels internally, freeing the PBO and PB1 pins for GPIO use. For proper self-powered Device operation, the VBUS value must still be monitored to assure that if the Host removes VBUS, the self-powered Device disables the D+/D- pull-up resistors. This function can be accomplished by connecting a standard GPIO to VBUS.

The termination resistors for the USB PHY have been added internally, and thus there is no need for external resistors. For a device, there is a 1.5 KOhm pull-up on the D+ and for a host there are 15 KOhm pull-downs on both D+ and D-.

Table 18-1. USB Signals (100LQFP)

Pin Name	Pin Number	Pin Mux / Pin Assignment	Pin Type	Buffer Type ^a	Description
USB0DM	68	PJ0	I/O	Analog	Bidirectional differential data pin (D- per USB specification) for USB0.
USB0DP	69	PJ1	I/O	Analog	Bidirectional differential data pin (D+ per USB specification) for USB0.
USB0EPEN	3 23 39 74	PD2 (8) PC6 (8) PF4 (8) PG4 (8)	0	TTL	Optionally used in Host mode to control an external power source to supply power to the USB bus.
USBOID	70	PB0	I	Analog	This signal senses the state of the USB ID signal. The USB PHY enables an integrated pull-up, and an external element (USB connector) indicates the initial state of the USB controller (pulled down is the A side of the cable and pulled up is the B side).
USB0PFLT	4 22 37 75	PD3 (8) PC7 (8) PF5 (8) PG5 (8)	I	TTL	Optionally used in Host mode by an external power source to indicate an error state by that power source.
USB0VBUS	71	PB1	I/O	Analog	This signal is used during the session request protocol. This signal allows the USB PHY to both sense the voltage level of VBUS, and pull up VBUS momentarily during VBUS pulsing.

a. The TTL designation indicates the pin has TTL-compatible voltage levels.

18.3 Functional Description

The Stellaris USB controller provides full OTG negotiation by supporting both the Session Request Protocol (SRP) and the Host Negotiation Protocol (HNP). The session request protocol allows devices on the B side of a cable to request the A side device turn on VBUS. The host negotiation protocol is used after the initial session request protocol has powered the bus and provides a method to determine which end of the cable will act as the Host controller. When the device is connected to non-OTG peripherals or devices, the controller can detect which cable end was used and provides a register to indicate if the controller should act as the Host or the Device controller. This indication and the mode of operation are handled automatically by the USB controller. This auto-detection allows the system to use a single A/B connector instead of having both A and B connectors in the system and supports full OTG negotiations with other OTG devices.

In addition, the USB controller provides support for connecting to non-OTG peripherals or Host controllers. The USB controller can be configured to act as either a dedicated Host or Device, in which case, the USB0VBUS and USB0ID signals can be used as GPIOs. However, when the USB controller is acting as a self-powered Device, a GPIO input or analog comparator input must be connected to VBUS and configured to generate an interrupt when the VBUS level drops. This interrupt is used to disable the pullup resistor on the USB0DP signal.

Note: When the USB module is in operation, MOSC must be the clock source, either with or without using the PLL, and the system clock must be at least 20 MHz.

18.3.1 Operation as a Device

This section describes the Stellaris USB controller's actions when it is being used as a USB Device. Before the USB controller's operating mode is changed from Device to Host or Host to Device, software must reset the USB controller by setting the USB0 bit in the **Software Reset Control 2**

(SRCR2) register (see page 447). IN endpoints, OUT endpoints, entry into and exit from SUSPEND mode, and recognition of Start of Frame (SOF) are all described.

When in Device mode, IN transactions are controlled by an endpoint's transmit interface and use the transmit endpoint registers for the given endpoint. OUT transactions are handled with an endpoint's receive interface and use the receive endpoint registers for the given endpoint.

When configuring the size of the FIFOs for endpoints, take into account the maximum packet size for an endpoint.

- **Bulk**. Bulk endpoints should be the size of the maximum packet (up to 64 bytes) or twice the maximum packet size if double buffering is used (described further in the following section).
- Interrupt. Interrupt endpoints should be the size of the maximum packet (up to 64 bytes) or twice the maximum packet size if double buffering is used.
- Isochronous. Isochronous endpoints are more flexible and can be up to 1023 bytes.
- **Control.** It is also possible to specify a separate control endpoint for a USB Device. However, in most cases the USB Device should use the dedicated control endpoint on the USB controller's endpoint 0.

18.3.1.1 Endpoints

When operating as a Device, the USB controller provides two dedicated control endpoints (IN and OUT) and 14 configurable endpoints (7 IN and 7 OUT) that can be used for communications with a Host controller. The endpoint number and direction associated with an endpoint is directly related to its register designation. For example, when the Host is transmitting to endpoint 1, all configuration and data is in the endpoint 1 transmit register interface.

Endpoint 0 is a dedicated control endpoint used for all control transactions to endpoint 0 during enumeration or when any other control requests are made to endpoint 0. Endpoint 0 uses the first 64 bytes of the USB controller's FIFO RAM as a shared memory for both IN and OUT transactions.

The remaining 14 endpoints can be configured as control, bulk, interrupt, or isochronous endpoints. They should be treated as 7 configurable IN and 7 configurable OUT endpoints. The endpoint pairs are not required to have the same type for their IN and OUT endpoint configuration. For example, the OUT portion of an endpoint pair could be a bulk endpoint, while the IN portion of that endpoint pair could be an interrupt endpoint. The address and size of the FIFOs attached to each endpoint can be modified to fit the application's needs.

18.3.1.2 IN Transactions as a Device

When operating as a USB Device, data for IN transactions is handled through the FIFOs attached to the transmit endpoints. The sizes of the FIFOs for the 7 configurable IN endpoints are determined by the **USB Transmit FIFO Start Address (USBTXFIFOADD)** register. The maximum size of a data packet that may be placed in a transmit endpoint's FIFO for transmission is programmable and is determined by the value written to the **USB Maximum Transmit Data Endpoint n (USBTXMAXPn)** register for that endpoint. The endpoint's FIFO can also be configured to use double-packet or single-packet buffering. When double-packet buffering is enabled, two data packets can be buffered in the FIFO, which also requires that the FIFO is at least two packets in size. When double-packet buffering is disabled, only one packet can be buffered, even if the packet size is less than half the FIFO size.

Note: The maximum packet size set for any endpoint must not exceed the FIFO size. The **USBTXMAXPn** register should not be written to while data is in the FIFO as unexpected results may occur.

Single-Packet Buffering

If the size of the transmit endpoint's FIFO is less than twice the maximum packet size for this endpoint (as set in the USB Transmit Dynamic FIFO Sizing (USBTXFIFOSZ) register), only one packet can be buffered in the FIFO and single-packet buffering is required. When each packet is completely loaded into the transmit FIFO, the TXRDY bit in the USB Transmit Control and Status Endpoint n Low (USBTXCSRLn) register must be set. If the AUTOSET bit in the USB Transmit Control and Status Endpoint n High (USBTXCSRHn) register is set, the TXRDY bit is automatically set when a maximum-sized packet is loaded into the FIFO. For packet sizes less than the maximum, the TXRDY bit must be set manually. When the TXRDY bit is set, either manually or automatically, the packet is ready to be sent. When the packet has been successfully sent, both TXRDY and FIFONE are cleared, and the appropriate transmit endpoint interrupt signaled. At this point, the next packet can be loaded into the FIFO.

Double-Packet Buffering

If the size of the transmit endpoint's FIFO is at least twice the maximum packet size for this endpoint, two packets can be buffered in the FIFO and double-packet buffering is allowed. As each packet is loaded into the transmit FIFO, the TXRDY bit in the USBTXCSRLn register must be set. If the AUTOSET bit in the USBTXCSRHn register is set, the TXRDY bit is automatically set when a maximum-sized packet is loaded into the FIFO. For packet sizes less than the maximum, TXRDY must be set manually. When the TXRDY bit is set, either manually or automatically, the packet is ready to be sent. After the first packet is loaded, TXRDY is immediately cleared and an interrupt is generated. A second packet can now be loaded into the transmit FIFO and TXRDY set again (either manually or automatically if the packet is the maximum size). At this point, both packets are ready to be sent. After each packet has been successfully sent, TXRDY is automatically cleared and the appropriate transmit endpoint interrupt signaled to indicate that another packet can now be loaded into the transmit FIFO. The state of the FIFONE bit in the USBTXCSRLn register at this point indicates how many packets may be loaded. If the FIFONE bit is set, then another packet is in the FIFO and only one more packet can be loaded. If the FIFONE bit is clear, then no packets are in the FIFO and two more packets can be loaded.

Note: Double-packet buffering is disabled if an endpoint's corresponding EPn bit is set in the USB Transmit Double Packet Buffer Disable (USBTXDPKTBUFDIS) register. This bit is set by default, so it must be cleared to enable double-packet buffering.

18.3.1.3 OUT Transactions as a Device

When in Device mode, OUT transactions are handled through the USB controller receive FIFOs. The sizes of the receive FIFOs for the 7 configurable OUT endpoints are determined by the USB Receive FIFO Start Address (USBRXFIFOADD) register. The maximum amount of data received by an endpoint in any packet is determined by the value written to the USB Maximum Receive Data Endpoint n (USBRXMAXPn) register for that endpoint. When double-packet buffering is enabled, two data packets can be buffered in the FIFO. When double-packet buffering is disabled, only one packet can be buffered even if the packet is less than half the FIFO size.

Note: In all cases, the maximum packet size must not exceed the FIFO size.

Single-Packet Buffering

If the size of the receive endpoint FIFO is less than twice the maximum packet size for an endpoint, only one data packet can be buffered in the FIFO and single-packet buffering is required. When a packet is received and placed in the receive FIFO, the RXRDY and FULL bits in the **USB Receive Control and Status Endpoint n Low (USBRXCSRLn)** register are set and the appropriate receive endpoint is signaled, indicating that a packet can now be unloaded from the FIFO. After the packet

has been unloaded, the RXRDY bit must be cleared in order to allow further packets to be received. This action also generates the acknowledge signaling to the Host controller. If the AUTOCL bit in the USB Receive Control and Status Endpoint n High (USBRXCSRHn) register is set and a maximum-sized packet is unloaded from the FIFO, the RXRDY and FULL bits are cleared automatically. For packet sizes less than the maximum, RXRDY must be cleared manually.

Double-Packet Buffering

If the size of the receive endpoint FIFO is at least twice the maximum packet size for the endpoint, two data packets can be buffered and double-packet buffering can be used. When the first packet is received and loaded into the receive FIFO, the RXRDY bit in the **USBRXCSRLn** register is set and the appropriate receive endpoint interrupt is signaled to indicate that a packet can now be unloaded from the FIFO.

Note: The FULL bit in **USBRXCSRLn** is not set when the first packet is received. It is only set if a second packet is received and loaded into the receive FIFO.

After each packet has been unloaded, the RXRDY bit must be cleared to allow further packets to be received. If the AUTOCL bit in the **USBRXCSRHn** register is set and a maximum-sized packet is unloaded from the FIFO, the RXRDY bit is cleared automatically. For packet sizes less than the maximum, RXRDY must be cleared manually. If the FULL bit is set when RXRDY is cleared, the USB controller first clears the FULL bit, then sets RXRDY again to indicate that there is another packet waiting in the FIFO to be unloaded.

Note: Double-packet buffering is disabled if an endpoint's corresponding EPn bit is set in the USB Receive Double Packet Buffer Disable (USBRXDPKTBUFDIS) register. This bit is set by default, so it must be cleared to enable double-packet buffering.

18.3.1.4 Scheduling

The Device has no control over the scheduling of transactions as scheduling is determined by the Host controller. The Stellaris USB controller can set up a transaction at any time. The USB controller waits for the request from the Host controller and generates an interrupt when the transaction is complete or if it was terminated due to some error. If the Host controller makes a request and the Device controller is not ready, the USB controller sends a busy response (NAK) to all requests until it is ready.

18.3.1.5 Additional Actions

The USB controller responds automatically to certain conditions on the USB bus or actions by the Host controller such as when the USB controller automatically stalls a control transfer or unexpected zero length OUT data packets.

Stalled Control Transfer

The USB controller automatically issues a STALL handshake to a control transfer under the following conditions:

- 1. The Host sends more data during an OUT data phase of a control transfer than was specified in the Device request during the SETUP phase. This condition is detected by the USB controller when the Host sends an OUT token (instead of an IN token) after the last OUT packet has been unloaded and the DATAEND bit in the USB Control and Status Endpoint 0 Low (USBCSRL0) register has been set.
- 2. The Host requests more data during an IN data phase of a control transfer than was specified in the Device request during the SETUP phase. This condition is detected by the USB controller

when the Host sends an IN token (instead of an OUT token) after the CPU has cleared TXRDY and set DATAEND in response to the ACK issued by the Host to what should have been the last packet.

- 3. The Host sends more than **USBRXMAXPn** bytes of data with an OUT data token.
- 4. The Host sends more than a zero length data packet for the OUT STATUS phase.

Zero Length OUT Data Packets

A zero-length OUT data packet is used to indicate the end of a control transfer. In normal operation, such packets should only be received after the entire length of the Device request has been transferred.

However, if the Host sends a zero-length OUT data packet before the entire length of Device request has been transferred, it is signaling the premature end of the transfer. In this case, the USB controller automatically flushes any IN token ready for the data phase from the FIFO and sets the DATAEND bit in the **USBCSRL0** register.

Setting the Device Address

When a Host is attempting to enumerate the USB Device, it requests that the Device change its address from zero to some other value. The address is changed by writing the value that the Host requested to the **USB Device Functional Address (USBFADDR)** register. However, care should be taken when writing to **USBFADDR** to avoid changing the address before the transaction is complete. This register should only be set after the SET_ADDRESS command is complete. Like all control transactions, the transaction is only complete after the Device has left the STATUS phase. In the case of a SET_ADDRESS command, the transaction is completed by responding to the IN request from the Host with a zero-byte packet. Once the Device has responded to the IN request, the **USBFADDR** register should be programmed to the new value as soon as possible to avoid missing any new commands sent to the new address.

Note: If the **USBFADDR** register is set to the new value as soon as the Device receives the OUT transaction with the SET_ADDRESS command in the packet, it changes the address during the control transfer. In this case, the Device does not receive the IN request that allows the USB transaction to exit the STATUS phase of the control transfer because it is sent to the old address. As a result, the Host does not get a response to the IN request, and the Host fails to enumerate the Device.

18.3.1.6 Device Mode SUSPEND

When no activity has occurred on the USB bus for 3 ms, the USB controller automatically enters SUSPEND mode. If the SUSPEND interrupt has been enabled in the **USB Interrupt Enable (USBIE)** register, an interrupt is generated at this time. When in SUSPEND mode, the PHY also goes into SUSPEND mode. When RESUME signaling is detected, the USB controller exits SUSPEND mode and takes the PHY out of SUSPEND. If the RESUME interrupt is enabled, an interrupt is generated. The USB controller can also be forced to exit SUSPEND mode by setting the RESUME bit in the **USB Power (USBPOWER)** register. When this bit is set, the USB controller exits SUSPEND mode and drives RESUME signaling onto the bus. The RESUME bit must be cleared after 10 ms (a maximum of 15 ms) to end RESUME signaling.

To meet USB power requirements, the controller can be put into Deep Sleep mode which keeps the controller in a static state. The USB controller is not able to Hibernate because all the internal states are lost as a result.

18.3.1.7 Start-of-Frame

When the USB controller is operating in Device mode, it receives a Start-Of-Frame (SOF) packet from the Host once every millisecond. When the SOF packet is received, the 11-bit frame number contained in the packet is written into the **USB Frame Value (USBFRAME)** register, and an SOF interrupt is also signaled and can be handled by the application. Once the USB controller has started to receive SOF packets, it expects one every millisecond. If no SOF packet is received after 1.00358 ms, the packet is assumed to have been lost, and the **USBFRAME** register is not updated. The USB controller continues and resynchronizes these pulses to the received SOF packets when these packets are successfully received again.

18.3.1.8 USB RESET

When the USB controller is in Device mode and a RESET condition is detected on the USB bus, the USB controller automatically performs the following actions:

- Clears the USBFADDR register.
- Clears the USB Endpoint Index (USBEPIDX) register.
- Flushes all endpoint FIFOs.
- Clears all control/status registers.
- Enables all endpoint interrupts.
- Generates a RESET interrupt.

When the application software driving the USB controller receives a RESET interrupt, any open pipes are closed and the USB controller waits for bus enumeration to begin.

18.3.1.9 Connect/Disconnect

The USB controller connection to the USB bus is handled by software. The USB PHY can be switched between normal mode and non-driving mode by setting or clearing the SOFTCONN bit of the USBPOWER register. When the SOFTCONN bit is set, the PHY is placed in its normal mode, and the USBODP/USBODM lines of the USB bus are enabled. At the same time, the USB controller is placed into a state, in which it does not respond to any USB signaling except a USB RESET.

When the SOFTCONN bit is cleared, the PHY is put into non-driving mode, USBODP and USBODM are tristated, and the USB controller appears to other devices on the USB bus as if it has been disconnected. The non-driving mode is the default so the USB controller appears disconnected until the SOFTCONN bit has been set. The application software can then choose when to set the PHY into its normal mode. Systems with a lengthy initialization procedure may use this to ensure that initialization is complete, and the system is ready to perform enumeration before connecting to the USB bus. Once the SOFTCONN bit has been set, the USB controller can be disconnected by clearing this bit.

Note: The USB controller does not generate an interrupt when the Device is connected to the Host. However, an interrupt is generated when the Host terminates a session.

18.3.2 Operation as a Host

When the Stellaris USB controller is operating in Host mode, it can either be used for point-to-point communications with another USB device or, when attached to a hub, for communication with multiple devices. Before the USB controller's operating mode is changed from Host to Device or

Device to Host, software must reset the USB controller by setting the USB0 bit in the **Software Reset Control 2 (SRCR2)** register (see page 447). Full-speed and low-speed USB devices are supported, both for point-to-point communication and for operation through a hub. The USB controller automatically carries out the necessary transaction translation needed to allow a low-speed or full-speed device to be used with a USB 2.0 hub. Control, bulk, isochronous, and interrupt transactions are supported. This section describes the USB controller's actions when it is being used as a USB Host. Configuration of IN endpoints, OUT endpoints, entry into and exit from SUSPEND mode, and RESET are all described.

When in Host mode, IN transactions are controlled by an endpoint's receive interface. All IN transactions use the receive endpoint registers and all OUT endpoints use the transmit endpoint registers for a given endpoint. As in Device mode, the FIFOs for endpoints should take into account the maximum packet size for an endpoint.

- **Bulk.** Bulk endpoints should be the size of the maximum packet (up to 64 bytes) or twice the maximum packet size if double buffering is used (described further in the following section).
- Interrupt. Interrupt endpoints should be the size of the maximum packet (up to 64 bytes) or twice the maximum packet size if double buffering is used.
- Isochronous. Isochronous endpoints are more flexible and can be up to 1023 bytes.
- **Control.** It is also possible to specify a separate control endpoint to communicate with a Device. However, in most cases the USB controller should use the dedicated control endpoint to communicate with a Device's endpoint 0.

18.3.2.1 Endpoints

The endpoint registers are used to control the USB endpoint interfaces which communicate with Device(s) that are connected. The endpoints consist of a dedicated control IN endpoint, a dedicated control OUT endpoint, 7 configurable OUT endpoints, and 7 configurable IN endpoints.

The dedicated control interface can only be used for control transactions to endpoint 0 of Devices. These control transactions are used during enumeration or other control functions that communicate using endpoint 0 of Devices. This control endpoint shares the first 64 bytes of the USB controller's FIFO RAM for IN and OUT transactions. The remaining IN and OUT interfaces can be configured to communicate with control, bulk, interrupt, or isochronous Device endpoints.

These USB interfaces can be used to simultaneously schedule as many as 7 independent OUT and 7 independent IN transactions to any endpoints on any Device. The IN and OUT controls are paired in three sets of registers. However, they can be configured to communicate with different types of endpoints and different endpoints on Devices. For example, the first pair of endpoint controls can be split so that the OUT portion is communicating with a Device's bulk OUT endpoint 1, while the IN portion is communicating with a Device's interrupt IN endpoint 2.

Before accessing any Device, whether for point-to-point communications or for communications via a hub, the relevant **USB Receive Functional Address Endpoint n (USBRXFUNCADDRn)** or **USB Transmit Functional Address Endpoint n (USBTXFUNCADDRn)** registers must be set for each receive or transmit endpoint to record the address of the Device being accessed.

The USB controller also supports connections to Devices through a USB hub by providing a register that specifies the hub address and port of each USB transfer. The FIFO address and size are customizable and can be specified for each USB IN and OUT transfer. Customization includes allowing one FIFO per transaction, sharing a FIFO across transactions, and allowing for double-buffered FIFOs.

18.3.2.2 IN Transactions as a Host

IN transactions are handled in a similar manner to the way in which OUT transactions are handled when the USB controller is in Device mode except that the transaction first must be initiated by setting the REQPKT bit in the USBCSRL0 register, indicating to the transaction scheduler that there is an active transaction on this endpoint. The transaction scheduler then sends an IN token to the target Device. When the packet is received and placed in the receive FIFO, the RXRDY bit in the USBCSRL0 register is set, and the appropriate receive endpoint interrupt is signaled to indicate that a packet can now be unloaded from the FIFO.

When the packet has been unloaded, RXRDY must be cleared. The AUTOCL bit in the USBRXCSRHn register can be used to have RXRDY automatically cleared when a maximum-sized packet has been unloaded from the FIFO. The AUTORQ bit in USBRXCSRHn causes the REQPKT bit to be automatically set when the RXRDY bit is cleared. The AUTOCL and AUTORQ bits can be used with µDMA accesses to perform complete bulk transfers without main processor intervention. When the RXRDY bit is cleared, the controller sends an acknowledge to the Device. When there is a known number of packets to be transferred, the USB Request Packet Count in Block Transfer Endpoint n (USBRQPKTCOUNTn) register associated with the endpoint should be configured to the number of packets to be transferred. The USB controller decrements the value in the USBRQPKTCOUNTn register following each request. When the USBRQPKTCOUNTn value decrements to 0, the AUTORQ bit is cleared to prevent any further transactions being attempted. For cases where the size of the transfer is unknown, USBRQPKTCOUNTn should be cleared. AUTORQ then remains set until cleared by the reception of a short packet (that is, less than the MAXLOAD value in the USBRXMAXPn register) such as may occur at the end of a bulk transfer.

If the Device responds to a bulk or interrupt IN token with a NAK, the USB Host controller keeps retrying the transaction until any NAK Limit that has been set has been reached. If the target Device responds with a STALL, however, the USB Host controller does not retry the transaction but sets the STALLED bit in the **USBCSRL0** register. If the target Device does not respond to the IN token within the required time, or the packet contained a CRC or bit-stuff error, the USB Host controller retries the transaction. If after three attempts the target Device has still not responded, the USB Host controller clears the REQPKT bit and sets the ERROR bit in the **USBCSRL0** register.

18.3.2.3 OUT Transactions as a Host

OUT transactions are handled in a similar manner to the way in which IN transactions are handled when the USB controller is in Device mode. The <code>TXRDY</code> bit in the <code>USBTXCSRLn</code> register must be set as each packet is loaded into the transmit FIFO. Again, setting the <code>AUTOSET</code> bit in the <code>USBTXCSRHn</code> register automatically sets <code>TXRDY</code> when a maximum-sized packet has been loaded into the FIFO. Furthermore, <code>AUTOSET</code> can be used with the μ DMA controller to perform complete bulk transfers without software intervention.

If the target Device responds to the OUT token with a NAK, the USB Host controller keeps retrying the transaction until the NAK Limit that has been set has been reached. However, if the target Device responds with a STALL, the USB controller does not retry the transaction but interrupts the main processor by setting the STALLED bit in the **USBTXCSRLn** register. If the target Device does not respond to the OUT token within the required time, or the packet contained a CRC or bit-stuff error, the USB Host controller retries the transaction. If after three attempts the target Device has still not responded, the USB controller flushes the FIFO and sets the ERROR bit in the **USBTXCSRLn** register.

18.3.2.4 Transaction Scheduling

Scheduling of transactions is handled automatically by the USB Host controller. The Host controller allows configuration of the endpoint communication scheduling based on the type of endpoint transaction. Interrupt transactions can be scheduled to occur in the range of every frame to every

255 frames in 1 frame increments. Bulk endpoints do not allow scheduling parameters, but do allow for a NAK timeout in the event an endpoint on a Device is not responding. Isochronous endpoints can be scheduled from every frame to every 2¹⁶ frames, in powers of 2.

The USB controller maintains a frame counter. If the target Device is a full-speed device, the USB controller automatically sends an SOF packet at the start of each frame and increments the frame counter. If the target Device is a low-speed device, a *K* state is transmitted on the bus to act as a *keep-alive* to stop the low-speed device from going into SUSPEND mode.

After the SOF packet has been transmitted, the USB Host controller cycles through all the configured endpoints looking for active transactions. An active transaction is defined as a receive endpoint for which the REQPKT bit is set or a transmit endpoint for which the TXRDY bit and/or the FIFONE bit is set.

An isochronous or interrupt transaction is started if the transaction is found on the first scheduler cycle of a frame and if the interval counter for that endpoint has counted down to zero. As a result, only one interrupt or isochronous transaction occurs per endpoint every n frames, where n is the interval set via the USB Host Transmit Interval Endpoint n (USBTXINTERVALn) or USB Host Receive Interval Endpoint n (USBRXINTERVALn) register for that endpoint.

An active bulk transaction starts immediately, provided sufficient time is left in the frame to complete the transaction before the next SOF packet is due. If the transaction must be retried (for example, because a NAK was received or the target Device did not respond), then the transaction is not retried until the transaction scheduler has first checked all the other endpoints for active transactions. This process ensures that an endpoint that is sending a lot of NAKs does not block other transactions on the bus. The controller also allows the user to specify a limit to the length of time for NAKs to be received from a target Device before the endpoint times out.

18.3.2.5 USB Hubs

The following setup requirements apply to the USB Host controller only if it is used with a USB hub. When a full- or low-speed Device is connected to the USB controller via a USB 2.0 hub, details of the hub address and the hub port also must be recorded in the corresponding USB Receive Hub Address Endpoint n (USBRXHUBADDRn) and USB Receive Hub Port Endpoint n (USBRXHUBPORTn) or the USB Transmit Hub Address Endpoint n (USBTXHUBADDRn) and USB Transmit Hub Port Endpoint n (USBTXHUBPORTn) registers. In addition, the speed at which the Device operates (full or low) must be recorded in the USB Type Endpoint 0 (USBTYPE0) (endpoint 0), USB Host Configure Transmit Type Endpoint n (USBTXTYPEn), or USB Host Configure Receive Type Endpoint n (USBRXTYPEn) registers for each endpoint that is accessed by the Device.

For hub communications, the settings in these registers record the current allocation of the endpoints to the attached USB Devices. To maximize the number of Devices supported, the USB Host controller allows this allocation to be changed dynamically by simply updating the address and speed information recorded in these registers. Any changes in the allocation of endpoints to Device functions must be made following the completion of any on-going transactions on the endpoints affected.

18.3.2.6 Babble

The USB Host controller does not start a transaction until the bus has been inactive for at least the minimum inter-packet delay. The controller also does not start a transaction unless it can be finished before the end of the frame. If the bus is still active at the end of a frame, then the USB Host controller assumes that the target Device to which it is connected has malfunctioned, and the USB controller suspends all transactions and generates a babble interrupt.

18.3.2.7 Host SUSPEND

If the SUSPEND bit in the **USBPOWER** register is set, the USB Host controller completes the current transaction then stops the transaction scheduler and frame counter. No further transactions are started and no SOF packets are generated.

To exit SUSPEND mode, set the RESUME bit and clear the SUSPEND bit. While the RESUME bit is set, the USB Host controller generates RESUME signaling on the bus. After 20 ms, the RESUME bit must be cleared, at which point the frame counter and transaction scheduler start. The Host supports the detection of a remote wake-up.

18.3.2.8 USB RESET

If the RESET bit in the **USBPOWER** register is set, the USB Host controller generates USB RESET signaling on the bus. The RESET bit must be set for at least 20 ms to ensure correct resetting of the target Device. After the CPU has cleared the bit, the USB Host controller starts its frame counter and transaction scheduler.

18.3.2.9 Connect/Disconnect

A session is started by setting the SESSION bit in the **USB Device Control (USBDEVCTL)** register, enabling the USB controller to wait for a Device to be connected. When a Device is detected, a connect interrupt is generated. The speed of the Device that has been connected can be determined by reading the **USBDEVCTL** register where the FSDEV bit is set for a full-speed Device, and the LSDEV bit is set for a low-speed Device. The USB controller must generate a RESET to the Device, and then the USB Host controller can begin Device enumeration. If the Device is disconnected while a session is in progress, a disconnect interrupt is generated.

18.3.3 OTG Mode

To conserve power, the USB On-The-Go (OTG) supplement allows VBUS to only be powered up when required and to be turned off when the bus is not in use. VBUS is always supplied by the A device on the bus. The USB OTG controller determines whether it is the A device or the B device by sampling the ID input from the PHY. This signal is pulled Low when an A-type plug is sensed (signifying that the USB OTG controller should act as the A device) but taken High when a B-type plug is sensed (signifying that the USB controller is a B device). Note that when switching between OTG A and OTG B, the USB controller retains all register contents.

18.3.3.1 Starting a Session

When the USB OTG controller is ready to start a session, the SESSION bit must be set in the USBDEVCTL register. The USB OTG controller then enables ID pin sensing. The ID input is either taken Low if an A-type connection is detected or High if a B-type connection is detected. The DEV bit in the USBDEVCTL register is also set to indicate whether the USB OTG controller has adopted the role of the A device or the B device. The USB OTG controller also provides an interrupt to indicate that ID pin sensing has completed and the mode value in the USBDEVCTL register is valid. This interrupt is enabled in the USBIDVIM register, and the status is checked in the USBIDVISC register. As soon as the USB controller has detected that it is on the A side of the cable, it must enable VBUS power within 100ms or the USB controller reverts to Device mode.

If the USB OTG controller is the A device, then the USB OTG controller enters Host mode (the A device is always the default Host), turns on VBUS, and waits for VBUS to go above the VBUS Valid threshold, as indicated by the VBUS bit in the **USBDEVCTL** register going to 0x3. The USB OTG controller then waits for a peripheral to be connected. When a peripheral is detected, a Connect interrupt is signaled and either the FSDEV or LSDEV bit in the **USBDEVCTL** register is set, depending whether a full-speed or a low-speed peripheral is detected. The USB controller then issues a RESET

to the connected Device. The SESSION bit in the **USBDEVCTL** register can be cleared to end a session. The USB OTG controller also automatically ends the session if babble is detected or if VBUS drops below session valid.

Note: The USB OTG controller may not remain in Host mode when connected to high-current devices. Some devices draw enough current to momentarily drop VBUS below the VBUS-valid level causing the controller to drop out of Host mode. The only way to get back into Host mode is to allow VBUS to go below the Session End level. In this situation, the device is causing VBUS to drop repeatedly and pull VBUS back low the next time VBUS is enabled.

In addition, the USB OTG controller may not remain in Host mode when a device is told that it can start using it's active configuration. At this point the device starts drawing more current and can also drop VBUS below VBUS valid.

If the USB OTG controller is the B device, then the USB OTG controller requests a session using the session request protocol defined in the USB On-The-Go supplement, that is, it first discharges VBUS. Then when VBUS has gone below the Session End threshold (VBUS bit in the **USBDEVCTL** register goes to 0x0) and the line state has been a single-ended zero for > 2 ms, the USB OTG controller pulses the data line, then pulses VBUS. At the end of the session, the SESSION bit is cleared either by the USB OTG controller or by the application software. The USB OTG controller then causes the PHY to switch out the pull-up resistor on D+, signaling the A device to end the session.

18.3.3.2 Detecting Activity

When the other device of the OTG setup wishes to start a session, it either raises VBUS above the Session Valid threshold if it is the A device, or if it is the B device, it pulses the data line then pulses VBUS. Depending on which of these actions happens, the USB controller can determine whether it is the A device or the B device in the current setup and act accordingly. If VBUS is raised above the Session Valid threshold, then the USB controller is the B device. The USB controller sets the SESSION bit in the USBDEVCTL register. When RESET signaling is detected on the bus, a RESET interrupt is signaled, which is interpreted as the start of a session.

The USB controller is in Device mode as the B device is the default mode. At the end of the session, the A device turns off the power to VBUS. When VBUS drops below the Session Valid threshold, the USB controller detects this drop and clears the SESSION bit to indicate that the session has ended, causing a disconnect interrupt to be signaled. If data line and VBUS pulsing is detected, then the USB controller is the A device. The controller generates a SESSION REQUEST interrupt to indicate that the B device is requesting a session. The SESSION bit in the USBDEVCTL register must be set to start a session.

18.3.3.3 Host Negotiation

When the USB controller is the A device, ID is Low, and the controller automatically enters Host mode when a session starts. When the USB controller is the B device, ID is High, and the controller automatically enters Device mode when a session starts. However, software can request that the USB controller become the Host by setting the Hostreq bit in the USBDEVCTL register. This bit can be set either at the same time as requesting a Session Start by setting the SESSION bit in the USBDEVCTL register or at any time after a session has started. When the USB controller next enters SUSPEND mode and if the Hostreq bit remains set, the controller enters Host mode and begins host negotiation (as specified in the USB On-The-Go supplement) by causing the PHY to disconnect the pull-up resistor on the D+ line, causing the A device to switch to Device mode and connect its own pull-up resistor. When the USB controller detects this, a Connect interrupt is generated and the RESET bit in the USBPOWER register is set to begin resetting the A device. The

USB controller begins this reset sequence automatically to ensure that RESET is started as required within 1 ms of the A device connecting its pull-up resistor. The main processor should wait at least 20 ms, then clear the RESET bit and enumerate the A device.

When the USB OTG controller B device has finished using the bus, the USB controller goes into SUSPEND mode by setting the SUSPEND bit in the **USBPOWER** register. The A device detects this and either terminates the session or reverts to Host mode. If the A device is USB OTG controller, it generates a Disconnect interrupt.

18.3.4 DMA Operation

The USB peripheral provides an interface connected to the μ DMA controller with separate channels for 3 transmit endpoints and 3 receive endpoints. Software selects which endpoints to service with the μ DMA channels using the **USB DMA Select (USBDMASEL)** register. The μ DMA operation of the USB is enabled through the **USBTXCSRHn** and **USBRXCSRHn** registers, for the TX and RX channels respectively. When μ DMA operation is enabled, the USB asserts a μ DMA request on the enabled receive or transmit channel when the associated FIFO can transfer data. When either FIFO can transfer data, the burst request for that channel is asserted. The μ DMA channel must be configured to operate in Basic mode, and the size of the μ DMA transfer must be restricted to whole multiples of the size of the USB FIFO. Both read and write transfers of the USB FIFOs using μ DMA must be configured in this manner. For example, if the USB endpoint is configured with a FIFO size of 64 bytes, the μ DMA channel can be used to transfer 64 bytes to or from the endpoint FIFO. If the number of bytes to transfer is less than 64, then a programmed I/O method must be used to copy the data to or from the FIFO.

If the DMAMOD bit in the **USBTXCSRHn/USBRXCSRHn** register is clear, an interrupt is generated after every packet is transferred, but the μ DMA continues transferring data. If the DMAMOD bit is set, an interrupt is generated only when the entire μ DMA transfer is complete. The interrupt occurs on the USB interrupt vector. Therefore, if interrupts are used for USB operation and the μ DMA is enabled, the USB interrupt handler must be designed to handle the μ DMA completion interrupt.

Care must be taken when using the μDMA to unload the receive FIFO as data is read from the receive FIFO in 4 byte chunks regardless of value of the MAXLOAD field in the **USBRXCSRHn** register. The RXRDY bit is cleared as follows.

Table 18-2. Remainder (MAXLOAD/4)

Value	Description
0	MAXLOAD = 64 bytes
1	MAXLOAD = 61 bytes
2	MAXLOAD = 62 bytes
3	MAXLOAD = 63 bytes

Table 18-3. Actual Bytes Read

Value	Description
0	MAXLOAD
1	MAXLOAD+3
2	MAXLOAD+2
3	MAXLOAD+1

Table 18-4. Packet Sizes That Clear RXRDY

Value	Description			
0	axload, maxload-1, maxload-2, maxload-3			
1	MAXLOAD			
2	MAXLOAD, MAXLOAD-1			
3	MAXLOAD, MAXLOAD-1, MAXLOAD-2			

To enable DMA operation for the endpoint receive channel, the DMAEN bit of the **USBRXCSRHn** register should be set. To enable DMA operation for the endpoint transmit channel, the DMAEN bit of the **USBTXCSRHn** register must be set.

See "Micro Direct Memory Access (μ DMA)" on page 582 for more details about programming the μ DMA controller.

18.4 Initialization and Configuration

To use the USB Controller, the peripheral clock must be enabled via the **RCGCUSB** register (see page 341). In addition, the clock to the appropriate GPIO module must be enabled via the **RCGCGPIO** register in the System Control module (see page 330). To find out which GPIO port to enable, refer to Table 23-4 on page 1358. Configure the PMCn fields in the **GPIOPCTL** register to assign the USB signals to the appropriate pins (see page 688 and Table 23-5 on page 1367).

The initial configuration in all cases requires that the processor enable the USB controller and USB controller's physical layer interface (PHY) before setting any registers. The next step is to enable the USB PLL so that the correct clocking is provided to the PHY. To ensure that voltage is not supplied to the bus incorrectly, the external power control signal, USB0EPEN, should be negated on start up by configuring the USB0EPEN and USB0PFLT pins to be controlled by the USB controller and not exhibit their default GPIO behavior.

When used in OTG mode, USB0VBUS and USB0ID do not require any configuration as they are dedicated pins for the USB controller and directly connect to the USB connector's VBUS and ID signals. If the USB controller is used as either a dedicated Host or Device, the DEVMODOTG and DEVMOD bits in the USB General-Purpose Control and Status (USBGPCS) register can be used to connect the USB0VBUS and USB0ID inputs to fixed levels internally, freeing the PB0 and PB1 pins for GPIO use. For proper self-powered Device operation, the VBUS value must still be monitored to assure that if the Host removes VBUS, the self-powered Device disables the D+/D- pull-up resistors. This function can be accomplished by connecting a standard GPIO to VBUS.

The termination resistors for the USB PHY have been added internally, and thus there is no need for external resistors. For a device, there is a 1.5 KOhm pull-up on the D+ and for a host there are 15 KOhm pull-downs on both D+ and D-.

18.4.1 Pin Configuration

When using the Device controller portion of the USB controller in a system that also provides Host functionality, the power to VBUS must be disabled to allow the external Host controller to supply power. Usually, the USB0EPEN signal is used to control the external regulator and should be negated to avoid having two devices driving the USB0VBUS power pin on the USB connector.

When the USB controller is acting as a Host, it is in control of two signals that are attached to an external voltage supply that provides power to VBUS. The Host controller uses the USB0EPEN signal to enable or disable power to the USB0VBUS pin on the USB connector. An input pin, USB0PFLT, provides feedback when there has been a power fault on VBUS. The USB0PFLT signal can be

configured to either automatically negate the USB0EPEN signal to disable power, and/or it can generate an interrupt to the interrupt controller to allow software to handle the power fault condition. The polarity and actions related to both USB0EPEN and USB0PFLT are fully configurable in the USB controller. The controller also provides interrupts on Device insertion and removal to allow the Host controller code to respond to these external events.

18.4.2 Endpoint Configuration

To start communication in Host or Device mode, the endpoint registers must first be configured. In Host mode, this configuration establishes a connection between an endpoint register and an endpoint on a Device. In Device mode, an endpoint must be configured before enumerating to the Host controller.

In both cases, the endpoint 0 configuration is limited because it is a fixed-function, fixed-FIFO-size endpoint. In Device and Host modes, the endpoint requires little setup but does require a software-based state machine to progress through the setup, data, and status phases of a standard control transaction. In Device mode, the configuration of the remaining endpoints is done once before enumerating and then only changed if an alternate configuration is selected by the Host controller. In Host mode, the endpoints must be configured to operate as control, bulk, interrupt or isochronous mode. Once the type of endpoint is configured, a FIFO area must be assigned to each endpoint. In the case of bulk, control and interrupt endpoints, each has a maximum of 64 bytes per transaction. Isochronous endpoints can have packets with up to 1023 bytes per packet. In either mode, the maximum packet size for the given endpoint must be set prior to sending or receiving data.

Configuring each endpoint's FIFO involves reserving a portion of the overall USB FIFO RAM to each endpoint. The total FIFO RAM available is 2 Kbytes with the first 64 bytes reserved for endpoint 0. The endpoint's FIFO must be at least as large as the maximum packet size. The FIFO can also be configured as a double-buffered FIFO so that interrupts occur at the end of each packet and allow filling the other half of the FIFO.

If operating as a Device, the USB Device controller's soft connect must be enabled when the Device is ready to start communications, indicating to the Host controller that the Device is ready to start the enumeration process. If operating as a Host controller, the Device soft connect must be disabled and power must be provided to VBUS via the USB0EPEN signal.

18.5 Register Map

Table 18-5 on page 1119 lists the registers. All addresses given are relative to the USB base address of 0x4005.0000. Note that the USB controller clock must be enabled before the registers can be programmed (see page 341). There must be a delay of 3 system clocks after the USB module clock is enabled before any USB module registers are accessed.

Table 18-5. Universal Serial Bus (USB) Controller Register Map

Offset	Name	Type	Reset	Description	See page
0x000	USBFADDR	R/W	0x00	USB Device Functional Address	1126
0x001	USBPOWER	R/W	0x20	USB Power	1127
0x002	USBTXIS	RO	0x0000	USB Transmit Interrupt Status	1130
0x004	USBRXIS	RO	0x0000	USB Receive Interrupt Status	1132
0x006	USBTXIE	R/W	0xFFFF	USB Transmit Interrupt Enable	1133

Table 18-5. Universal Serial Bus (USB) Controller Register Map (continued)

Offset	Name	Туре	Reset	Description	See page
0x008	USBRXIE	R/W	0xFFFE	USB Receive Interrupt Enable	1135
0x00A	USBIS	RO	0x00	USB General Interrupt Status	1136
0x00B	USBIE	R/W	0x06	USB Interrupt Enable	1139
0x00C	USBFRAME	RO	0x0000	USB Frame Value	1142
0x00E	USBEPIDX	R/W	0x00	USB Endpoint Index	1143
0x00F	USBTEST	R/W	0x00	USB Test Mode	1144
0x020	USBFIFO0	R/W	0x0000.0000	USB FIFO Endpoint 0	1146
0x024	USBFIFO1	R/W	0x0000.0000	USB FIFO Endpoint 1	1146
0x028	USBFIFO2	R/W	0x0000.0000	USB FIFO Endpoint 2	1146
0x02C	USBFIFO3	R/W	0x0000.0000	USB FIFO Endpoint 3	1146
0x030	USBFIFO4	R/W	0x0000.0000	USB FIFO Endpoint 4	1146
0x034	USBFIFO5	R/W	0x0000.0000	USB FIFO Endpoint 5	1146
0x038	USBFIFO6	R/W	0x0000.0000	USB FIFO Endpoint 6	1146
0x03C	USBFIF07	R/W	0x0000.0000	USB FIFO Endpoint 7	1146
0x060	USBDEVCTL	R/W	0x80	USB Device Control	1147
0x062	USBTXFIFOSZ	R/W	0x00	USB Transmit Dynamic FIFO Sizing	1149
0x063	USBRXFIFOSZ	R/W	0x00	USB Receive Dynamic FIFO Sizing	1149
0x064	USBTXFIFOADD	R/W	0x0000	USB Transmit FIFO Start Address	1150
0x066	USBRXFIFOADD	R/W	0x0000	USB Receive FIFO Start Address	1150
0x07A	USBCONTIM	R/W	0x5C	USB Connect Timing	1151
0x07B	USBVPLEN	R/W	0x3C	USB OTG VBUS Pulse Timing	1152
0x07D	USBFSEOF	R/W	0x77	USB Full-Speed Last Transaction to End of Frame Timing	1153
0x07E	USBLSEOF	R/W	0x72	USB Low-Speed Last Transaction to End of Frame Timing	1154
0x080	USBTXFUNCADDR0	R/W	0x00	USB Transmit Functional Address Endpoint 0	1155
0x082	USBTXHUBADDR0	R/W	0x00	USB Transmit Hub Address Endpoint 0	1156
0x083	USBTXHUBPORT0	R/W	0x00	USB Transmit Hub Port Endpoint 0	1157
0x088	USBTXFUNCADDR1	R/W	0x00	USB Transmit Functional Address Endpoint 1	1155
A80x0	USBTXHUBADDR1	R/W	0x00	USB Transmit Hub Address Endpoint 1	1156
0x08B	USBTXHUBPORT1	R/W	0x00	USB Transmit Hub Port Endpoint 1	1157
0x08C	USBRXFUNCADDR1	R/W	0x00	USB Receive Functional Address Endpoint 1	1158
0x08E	USBRXHUBADDR1	R/W	0x00	USB Receive Hub Address Endpoint 1	1159

Table 18-5. Universal Serial Bus (USB) Controller Register Map (continued)

Offset	Name	Туре	Reset	Description	See page
0x08F	USBRXHUBPORT1	R/W	0x00	USB Receive Hub Port Endpoint 1	1160
0x090	USBTXFUNCADDR2	R/W	0x00	USB Transmit Functional Address Endpoint 2	1155
0x092	USBTXHUBADDR2	R/W	0x00	USB Transmit Hub Address Endpoint 2	1156
0x093	USBTXHUBPORT2	R/W	0x00	USB Transmit Hub Port Endpoint 2	1157
0x094	USBRXFUNCADDR2	R/W	0x00	USB Receive Functional Address Endpoint 2	1158
0x096	USBRXHUBADDR2	R/W	0x00	USB Receive Hub Address Endpoint 2	1159
0x097	USBRXHUBPORT2	R/W	0x00	USB Receive Hub Port Endpoint 2	1160
0x098	USBTXFUNCADDR3	R/W	0x00	USB Transmit Functional Address Endpoint 3	1155
0x09A	USBTXHUBADDR3	R/W	0x00	USB Transmit Hub Address Endpoint 3	1156
0x09B	USBTXHUBPORT3	R/W	0x00	USB Transmit Hub Port Endpoint 3	1157
0x09C	USBRXFUNCADDR3	R/W	0x00	USB Receive Functional Address Endpoint 3	1158
0x09E	USBRXHUBADDR3	R/W	0x00	USB Receive Hub Address Endpoint 3	1159
0x09F	USBRXHUBPORT3	R/W	0x00	USB Receive Hub Port Endpoint 3	1160
0x0A0	USBTXFUNCADDR4	R/W	0x00	USB Transmit Functional Address Endpoint 4	1155
0x0A2	USBTXHUBADDR4	R/W	0x00	USB Transmit Hub Address Endpoint 4	1156
0x0A3	USBTXHUBPORT4	R/W	0x00	USB Transmit Hub Port Endpoint 4	1157
0x0A4	USBRXFUNCADDR4	R/W	0x00	USB Receive Functional Address Endpoint 4	1158
0x0A6	USBRXHUBADDR4	R/W	0x00	USB Receive Hub Address Endpoint 4	1159
0x0A7	USBRXHUBPORT4	R/W	0x00	USB Receive Hub Port Endpoint 4	1160
0x0A8	USBTXFUNCADDR5	R/W	0x00	USB Transmit Functional Address Endpoint 5	1155
0x0AA	USBTXHUBADDR5	R/W	0x00	USB Transmit Hub Address Endpoint 5	1156
0x0AB	USBTXHUBPORT5	R/W	0x00	USB Transmit Hub Port Endpoint 5	1157
0x0AC	USBRXFUNCADDR5	R/W	0x00	USB Receive Functional Address Endpoint 5	1158
0x0AE	USBRXHUBADDR5	R/W	0x00	USB Receive Hub Address Endpoint 5	1159
0x0AF	USBRXHUBPORT5	R/W	0x00	USB Receive Hub Port Endpoint 5	1160
0x0B0	USBTXFUNCADDR6	R/W	0x00	USB Transmit Functional Address Endpoint 6	1155
0x0B2	USBTXHUBADDR6	R/W	0x00	USB Transmit Hub Address Endpoint 6	1156
0x0B3	USBTXHUBPORT6	R/W	0x00	USB Transmit Hub Port Endpoint 6	1157
0x0B4	USBRXFUNCADDR6	R/W	0x00	USB Receive Functional Address Endpoint 6	1158
0x0B6	USBRXHUBADDR6	R/W	0x00	USB Receive Hub Address Endpoint 6	1159
0x0B7	USBRXHUBPORT6	R/W	0x00	USB Receive Hub Port Endpoint 6	1160
0x0B8	USBTXFUNCADDR7	R/W	0x00	USB Transmit Functional Address Endpoint 7	1155

Table 18-5. Universal Serial Bus (USB) Controller Register Map (continued)

Offset	Name	Туре	Reset	Description	See page
0x0BA	USBTXHUBADDR7	R/W	0x00	USB Transmit Hub Address Endpoint 7	1156
0x0BB	USBTXHUBPORT7	R/W	0x00	USB Transmit Hub Port Endpoint 7	1157
0x0BC	USBRXFUNCADDR7	R/W	0x00	USB Receive Functional Address Endpoint 7	1158
0x0BE	USBRXHUBADDR7	R/W	0x00	USB Receive Hub Address Endpoint 7	1159
0x0BF	USBRXHUBPORT7	R/W	0x00	USB Receive Hub Port Endpoint 7	1160
0x102	USBCSRL0	W1C	0x00	USB Control and Status Endpoint 0 Low	1162
0x103	USBCSRH0	W1C	0x00	USB Control and Status Endpoint 0 High	1166
0x108	USBCOUNT0	RO	0x00	USB Receive Byte Count Endpoint 0	1168
0x10A	USBTYPE0	R/W	0x00	USB Type Endpoint 0	1169
0x10B	USBNAKLMT	R/W	0x00	USB NAK Limit	1170
0x110	USBTXMAXP1	R/W	0x0000	USB Maximum Transmit Data Endpoint 1	1161
0x112	USBTXCSRL1	R/W	0x00	USB Transmit Control and Status Endpoint 1 Low	1171
0x113	USBTXCSRH1	R/W	0x00	USB Transmit Control and Status Endpoint 1 High	1175
0x114	USBRXMAXP1	R/W	0x0000	USB Maximum Receive Data Endpoint 1	1179
0x116	USBRXCSRL1	R/W	0x00	USB Receive Control and Status Endpoint 1 Low	1180
0x117	USBRXCSRH1	R/W	0x00	USB Receive Control and Status Endpoint 1 High	1185
0x118	USBRXCOUNT1	RO	0x0000	USB Receive Byte Count Endpoint 1	1189
0x11A	USBTXTYPE1	R/W	0x00	USB Host Transmit Configure Type Endpoint 1	1190
0x11B	USBTXINTERVAL1	R/W	0x00	USB Host Transmit Interval Endpoint 1	1192
0x11C	USBRXTYPE1	R/W	0x00	USB Host Configure Receive Type Endpoint 1	1193
0x11D	USBRXINTERVAL1	R/W	0x00	USB Host Receive Polling Interval Endpoint 1	1195
0x120	USBTXMAXP2	R/W	0x0000	USB Maximum Transmit Data Endpoint 2	1161
0x122	USBTXCSRL2	R/W	0x00	USB Transmit Control and Status Endpoint 2 Low	1171
0x123	USBTXCSRH2	R/W	0x00	USB Transmit Control and Status Endpoint 2 High	1175
0x124	USBRXMAXP2	R/W	0x0000	USB Maximum Receive Data Endpoint 2	1179
0x126	USBRXCSRL2	R/W	0x00	USB Receive Control and Status Endpoint 2 Low	1180
0x127	USBRXCSRH2	R/W	0x00	USB Receive Control and Status Endpoint 2 High	1185
0x128	USBRXCOUNT2	RO	0x0000	USB Receive Byte Count Endpoint 2	1189
0x12A	USBTXTYPE2	R/W	0x00	USB Host Transmit Configure Type Endpoint 2	1190
0x12B	USBTXINTERVAL2	R/W	0x00	USB Host Transmit Interval Endpoint 2	1192
0x12C	USBRXTYPE2	R/W	0x00	USB Host Configure Receive Type Endpoint 2	1193
0x12D	USBRXINTERVAL2	R/W	0x00	USB Host Receive Polling Interval Endpoint 2	1195

Table 18-5. Universal Serial Bus (USB) Controller Register Map (continued)

Offset	Name	Туре	Reset	Description	See page
0x130	USBTXMAXP3	R/W	0x0000	USB Maximum Transmit Data Endpoint 3	1161
0x132	USBTXCSRL3	R/W	0x00	USB Transmit Control and Status Endpoint 3 Low	1171
0x133	USBTXCSRH3	R/W	0x00	USB Transmit Control and Status Endpoint 3 High	1175
0x134	USBRXMAXP3	R/W	0x0000	USB Maximum Receive Data Endpoint 3	1179
0x136	USBRXCSRL3	R/W	0x00	USB Receive Control and Status Endpoint 3 Low	1180
0x137	USBRXCSRH3	R/W	0x00	USB Receive Control and Status Endpoint 3 High	1185
0x138	USBRXCOUNT3	RO	0x0000	USB Receive Byte Count Endpoint 3	1189
0x13A	USBTXTYPE3	R/W	0x00	USB Host Transmit Configure Type Endpoint 3	1190
0x13B	USBTXINTERVAL3	R/W	0x00	USB Host Transmit Interval Endpoint 3	1192
0x13C	USBRXTYPE3	R/W	0x00	USB Host Configure Receive Type Endpoint 3	1193
0x13D	USBRXINTERVAL3	R/W	0x00	USB Host Receive Polling Interval Endpoint 3	1195
0x140	USBTXMAXP4	R/W	0x0000	USB Maximum Transmit Data Endpoint 4	1161
0x142	USBTXCSRL4	R/W	0x00	USB Transmit Control and Status Endpoint 4 Low	1171
0x143	USBTXCSRH4	R/W	0x00	USB Transmit Control and Status Endpoint 4 High	1175
0x144	USBRXMAXP4	R/W	0x0000	USB Maximum Receive Data Endpoint 4	1179
0x146	USBRXCSRL4	R/W	0x00	USB Receive Control and Status Endpoint 4 Low	1180
0x147	USBRXCSRH4	R/W	0x00	USB Receive Control and Status Endpoint 4 High	1185
0x148	USBRXCOUNT4	RO	0x0000	USB Receive Byte Count Endpoint 4	1189
0x14A	USBTXTYPE4	R/W	0x00	USB Host Transmit Configure Type Endpoint 4	1190
0x14B	USBTXINTERVAL4	R/W	0x00	USB Host Transmit Interval Endpoint 4	1192
0x14C	USBRXTYPE4	R/W	0x00	USB Host Configure Receive Type Endpoint 4	1193
0x14D	USBRXINTERVAL4	R/W	0x00	USB Host Receive Polling Interval Endpoint 4	1195
0x150	USBTXMAXP5	R/W	0x0000	USB Maximum Transmit Data Endpoint 5	1161
0x152	USBTXCSRL5	R/W	0x00	USB Transmit Control and Status Endpoint 5 Low	1171
0x153	USBTXCSRH5	R/W	0x00	USB Transmit Control and Status Endpoint 5 High	1175
0x154	USBRXMAXP5	R/W	0x0000	USB Maximum Receive Data Endpoint 5	1179
0x156	USBRXCSRL5	R/W	0x00	USB Receive Control and Status Endpoint 5 Low	1180
0x157	USBRXCSRH5	R/W	0x00	USB Receive Control and Status Endpoint 5 High	1185
0x158	USBRXCOUNT5	RO	0x0000	USB Receive Byte Count Endpoint 5	1189
0x15A	USBTXTYPE5	R/W	0x00	USB Host Transmit Configure Type Endpoint 5	1190
0x15B	USBTXINTERVAL5	R/W	0x00	USB Host Transmit Interval Endpoint 5	1192
0x15C	USBRXTYPE5	R/W	0x00	USB Host Configure Receive Type Endpoint 5	1193

Table 18-5. Universal Serial Bus (USB) Controller Register Map (continued)

Offset	Name	Туре	Reset	Description	See page
0x15D	USBRXINTERVAL5	R/W	0x00	USB Host Receive Polling Interval Endpoint 5	1195
0x160	USBTXMAXP6	R/W	0x0000	USB Maximum Transmit Data Endpoint 6	1161
0x162	USBTXCSRL6	R/W	0x00	USB Transmit Control and Status Endpoint 6 Low	1171
0x163	USBTXCSRH6	R/W	0x00	USB Transmit Control and Status Endpoint 6 High	1175
0x164	USBRXMAXP6	R/W	0x0000	USB Maximum Receive Data Endpoint 6	1179
0x166	USBRXCSRL6	R/W	0x00	USB Receive Control and Status Endpoint 6 Low	1180
0x167	USBRXCSRH6	R/W	0x00	USB Receive Control and Status Endpoint 6 High	1185
0x168	USBRXCOUNT6	RO	0x0000	USB Receive Byte Count Endpoint 6	1189
0x16A	USBTXTYPE6	R/W	0x00	USB Host Transmit Configure Type Endpoint 6	1190
0x16B	USBTXINTERVAL6	R/W	0x00	USB Host Transmit Interval Endpoint 6	1192
0x16C	USBRXTYPE6	R/W	0x00	USB Host Configure Receive Type Endpoint 6	1193
0x16D	USBRXINTERVAL6	R/W	0x00	USB Host Receive Polling Interval Endpoint 6	1195
0x170	USBTXMAXP7	R/W	0x0000	USB Maximum Transmit Data Endpoint 7	1161
0x172	USBTXCSRL7	R/W	0x00	USB Transmit Control and Status Endpoint 7 Low	1171
0x173	USBTXCSRH7	R/W	0x00	USB Transmit Control and Status Endpoint 7 High	1175
0x174	USBRXMAXP7	R/W	0x0000	USB Maximum Receive Data Endpoint 7	1179
0x176	USBRXCSRL7	R/W	0x00	USB Receive Control and Status Endpoint 7 Low	1180
0x177	USBRXCSRH7	R/W	0x00	USB Receive Control and Status Endpoint 7 High	1185
0x178	USBRXCOUNT7	RO	0x0000	USB Receive Byte Count Endpoint 7	1189
0x17A	USBTXTYPE7	R/W	0x00	USB Host Transmit Configure Type Endpoint 7	1190
0x17B	USBTXINTERVAL7	R/W	0x00	USB Host Transmit Interval Endpoint 7	1192
0x17C	USBRXTYPE7	R/W	0x00	USB Host Configure Receive Type Endpoint 7	1193
0x17D	USBRXINTERVAL7	R/W	0x00	USB Host Receive Polling Interval Endpoint 7	1195
0x304	USBRQPKTCOUNT1	R/W	0x0000	USB Request Packet Count in Block Transfer Endpoint 1	1196
0x308	USBRQPKTCOUNT2	R/W	0x0000	USB Request Packet Count in Block Transfer Endpoint 2	1196
0x30C	USBRQPKTCOUNT3	R/W	0x0000	USB Request Packet Count in Block Transfer Endpoint 3	1196
0x310	USBRQPKTCOUNT4	R/W	0x0000	USB Request Packet Count in Block Transfer Endpoint 4	1196
0x314	USBRQPKTCOUNT5	R/W	0x0000	USB Request Packet Count in Block Transfer Endpoint 5	1196
0x318	USBRQPKTCOUNT6	R/W	0x0000	USB Request Packet Count in Block Transfer Endpoint 6	1196

Table 18-5. Universal Serial Bus (USB) Controller Register Map (continued)

Offset	Name	Type	Reset	Description	See page
0x31C	USBRQPKTCOUNT7	R/W	0x0000	USB Request Packet Count in Block Transfer Endpoint 7	1196
0x340	USBRXDPKTBUFDIS	R/W	0x0000	USB Receive Double Packet Buffer Disable	1197
0x342	USBTXDPKTBUFDIS	R/W	0x0000	USB Transmit Double Packet Buffer Disable	1198
0x400	USBEPC	R/W	0x0000.0000	USB External Power Control	1199
0x404	USBEPCRIS	RO	0x0000.0000	USB External Power Control Raw Interrupt Status	1202
0x408	USBEPCIM	R/W	0x0000.0000	USB External Power Control Interrupt Mask	1203
0x40C	USBEPCISC	R/W	0x0000.0000	USB External Power Control Interrupt Status and Clear	1204
0x410	USBDRRIS	RO	0x0000.0000	USB Device RESUME Raw Interrupt Status	1205
0x414	USBDRIM	R/W	0x0000.0000	USB Device RESUME Interrupt Mask	1206
0x418	USBDRISC	W1C	0x0000.0000	USB Device RESUME Interrupt Status and Clear	1207
0x41C	USBGPCS	R/W	0x0000.0003	USB General-Purpose Control and Status	1208
0x430	USBVDC	R/W	0x0000.0000	USB VBUS Droop Control	1209
0x434	USBVDCRIS	RO	0x0000.0000	USB VBUS Droop Control Raw Interrupt Status	1210
0x438	USBVDCIM	R/W	0x0000.0000	USB VBUS Droop Control Interrupt Mask	1211
0x43C	USBVDCISC	R/W	0x0000.0000	USB VBUS Droop Control Interrupt Status and Clear	1212
0x444	USBIDVRIS	RO	0x0000.0000	USB ID Valid Detect Raw Interrupt Status	1213
0x448	USBIDVIM	R/W	0x0000.0000	USB ID Valid Detect Interrupt Mask	1214
0x44C	USBIDVISC	R/W1C	0x0000.0000	USB ID Valid Detect Interrupt Status and Clear	1215
0x450	USBDMASEL	R/W	0x0033.2211	USB DMA Select	1216
0xFC0	USBPP	RO	0x0000.10D0	USB Peripheral Properties	1218

18.6 Register Descriptions

The LM4F232H5QC USB controller has On-The-Go (OTG) capabilities as specified in the USB0 bit field in the **DC6** register (see page 435).

OTG B /

This icon indicates that the register is used in OTG B or Device mode. Some registers are used for both Host and Device mode and may have different bit definitions depending on the mode.

OTG A /

This icon indicates that the register is used in OTG A or Host mode. Some registers are used for both Host and Device mode and may have different bit definitions depending on the mode. The USB controller is in OTG B or Device mode upon reset, so the reset values shown for these registers apply to the Device mode definition.

OTG

This icon indicates that the register is used for OTG-specific functions such as ID detection and negotiation. Once OTG negotiation is complete, then the USB controller registers are used according to their Host or Device mode meanings depending on whether the OTG negotiations made the USB controller OTG A (Host) or OTG B (Device).

Register 1: USB Device Functional Address (USBFADDR), offset 0x000




USBFADDR is an 8-bit register that contains the 7-bit address of the Device part of the transaction.

When the USB controller is being used in Device mode (the HOST bit in the **USBDEVCTL** register is clear), this register must be written with the address received through a SET_ADDRESS command, which is then used for decoding the function address in subsequent token packets.

Important: See the section called "Setting the Device Address" on page 1110 for special considerations when writing this register.

USB Device Functional Address (USBFADDR)

Base 0x4005.0000 Offset 0x000 Type R/W, reset 0x00



Bit/Field	Name	Type	Reset	Description
7	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
6:0	FUNCADDR	R/W	0x00	Function Address

Function Address of Device as received through SET_ADDRESS.

Register 2: USB Power (USBPOWER), offset 0x001




USBPOWER is an 8-bit register used for controlling SUSPEND and RESUME signaling and some basic operational aspects of the USB controller.



OTG A / Host Mode

USB Power (USBPOWER)

Base 0x4005.0000 Offset 0x001 Type R/W, reset 0x20



Bit/Field	Name	Туре	Reset	Description
7:4	reserved	RO	0x2	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
3	RESET	R/W	0	RESET Signaling
				Value Description 0 Ends RESET signaling on the bus. 1 Enables RESET signaling on the bus.
2	RESUME	R/W	0	RESUME Signaling Value Description 0 Ends RESUME signaling on the bus.
				 Enables RESUME signaling when the Device is in SUSPEND mode.
				This bit must be cleared by software 20 ms after being set.
1	SUSPEND	R/W1S	0	SUSPEND Mode
				Value Description 0 No effect.

Enables SUSPEND mode.

Bit/Field	Name	Type	Reset	Description
0	PWRDNPHY	R/W	0	Power Down PHY
				Value Description
				0 No effect.
				1 Powers down the internal USB PHY.

OTG B / Device Mode

USB Power (USBPOWER)

Base 0x4005.0000 Offset 0x001 Type R/W, reset 0x20



Bit/Field	Name	Туре	Reset	Description
7	ISOUP	R/W	0	Isochronous Update
				 Value Description No effect. The USB controller waits for an SOF token from the time the TXRDY bit is set in the USBTXCSRLn register before sending the packet. If an IN token is received before an SOF token, then a zero-length data packet is sent. Note: This bit is only valid for isochronous transfers.
6	SOFTCONN	R/W	0	Note: This bit is only valid for isochronous transfers. Soft Connect/Disconnect Value Description 0 The USB D+/D- lines are tri-stated. 1 The USB D+/D- lines are enabled.
5:4	reserved	RO	0x2	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
3	RESET	RO	0	Value Description RESET signaling is not present on the bus. RESET signaling is present on the bus.

Bit/Field	Name	Туре	Reset	Description
2	RESUME	R/W	0	RESUME Signaling
				Value Description 0 Ends RESUME signaling on the bus.
				 Enables RESUME signaling when the Device is in SUSPEND mode.
				This bit must be cleared by software 10 ms (a maximum of 15 ms) after being set.
1	SUSPEND	RO	0	SUSPEND Mode
				Value Description
				0 This bit is cleared when software reads the interrupt register or sets the RESUME bit above.
				1 The USB controller is in SUSPEND mode.
0	PWRDNPHY	R/W	0	Power Down PHY
				Value Description
				0 No effect.
				1 Powers down the internal USB PHY.

Register 3: USB Transmit Interrupt Status (USBTXIS), offset 0x002

Important: This register is read-sensitive. See the register description for details.

OTG A / Host



USBTXIS is a 16-bit read-only register that indicates which interrupts are currently active for endpoint 0 and the transmit endpoints 1–7. The meaning of the EPn bits in this register is based on the mode of the device. The EP1 through EP7 bits always indicate that the USB controller is sending data; however, in Host mode, the bits refer to OUT endpoints; while in Device mode, the bits refer to IN endpoints. The EP0 bit is special in Host and Device modes and indicates that either a control IN or control OUT endpoint has generated an interrupt.

Note: Bits relating to endpoints that have not been configured always return 0. Note also that all active interrupts are cleared when this register is read.

USB Transmit Interrupt Status (USBTXIS)

Base 0x4005.0000 Offset 0x002 Type RO, reset 0x0000



Bit/Field	Name	Type	Reset	Description
15:8	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
7	EP7	RO	0	TX Endpoint 7 Interrupt
				Value Description 0 No interrupt.
				1 The Endpoint 7 transmit interrupt is asserted.
6	EP6	RO	0	TX Endpoint 6 Interrupt Same description as EP7.
5	EP5	RO	0	TX Endpoint 5 Interrupt Same description as EP7.
4	EP4	RO	0	TX Endpoint 4 Interrupt Same description as EP7.
3	EP3	RO	0	TX Endpoint 3 Interrupt Same description as EP7.
2	EP2	RO	0	TX Endpoint 2 Interrupt Same description as EP7.
1	EP1	RO	0	TX Endpoint 1 Interrupt Same description as EP7.

Bit/Field	Name	Туре	Reset	Description
0	EP0	RO	0	TX and RX Endpoint 0 Interrupt
				Value Description
				0 No interrupt.
				1 The Endpoint 0 transmit and receive interrupt is asserted.

February 20, 2013 1131

Register 4: USB Receive Interrupt Status (USBRXIS), offset 0x004

Important: This register is read-sensitive. See the register description for details.

OTG A /

USBRXIS is a 16-bit read-only register that indicates which of the interrupts for receive endpoints 1–7 are currently active.

Note: Bits relating to endpoints that have not been configured always return 0. Note also that all active interrupts are cleared when this register is read.

OTG B /
Device

USB Receive Interrupt Status (USBRXIS)

Base 0x4005.0000 Offset 0x004 Type RO, reset 0x0000

	15	14	13	12	11	10	9	8	7	6	5	4	3	2	1	0	
	reserved							EP7	EP6	EP5	EP4	EP3	EP2	EP1	reserved		
Туре	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	
Docot	Λ	0	Λ	0	Λ	Λ	Λ	Λ	Λ	Λ	Λ	Λ	Λ	Λ	Λ	Λ	

Bit/Field	Name	Type	Reset	Description
15:8	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
7	EP7	RO	0	RX Endpoint 7 Interrupt Value Description 0 No interrupt. 1 The Endpoint 7 transmit interrupt is asserted.
6	EP6	RO	0	RX Endpoint 6 Interrupt Same description as EP7.
5	EP5	RO	0	RX Endpoint 5 Interrupt Same description as EP7.
4	EP4	RO	0	RX Endpoint 4 Interrupt Same description as EP7.
3	EP3	RO	0	RX Endpoint 3 Interrupt Same description as EP7.
2	EP2	RO	0	RX Endpoint 2 Interrupt Same description as EP7
1	EP1	RO	0	RX Endpoint 1 Interrupt Same description as EP7.
0	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.

Register 5: USB Transmit Interrupt Enable (USBTXIE), offset 0x006



USBTXIE is a 16-bit register that provides interrupt enable bits for the interrupts in the **USBTXIS** register. When a bit is set, the USB interrupt is asserted to the interrupt controller when the corresponding interrupt bit in the **USBTXIS** register is set. When a bit is cleared, the interrupt in the **USBTXIS** register is still set but the USB interrupt to the interrupt controller is not asserted. On reset, all interrupts are enabled.

OTG B / Device

USB Transmit Interrupt Enable (USBTXIE)

Base 0x4005.0000

Туре	R/W, rese	Offset oxFFFF														
	15	14	13	12	11	10	9	8	7	6	5	4	3	2	1	0
		'	'	rese	rved				EP7	EP6	EP5	EP4	EP3	EP2	EP1	EP0
Type Reset	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	R/W 1	R/W 1	R/W 1	R/W 1	R/W 1	R/W 1	R/W 1	R/W 1
E	Bit/Field		Nam	e	Ту	ре	Reset	Des	cription							
	15:8		reserv	ed .	R	0	0	com	ware should be s	with fut	ure prod	ucts, the	value of	a reserv	•	
	7		EP7	7	R/	W	1	TXI	Endpoint	7 Interro	upt Enat	ole				
								Val	ue Desc	ription						
								0		EP7 tran upt cont		rrupt is s	suppress	ed and r	not sent	to the
								1				the inter ter is set		itroller w	hen the	E₽7 bit
	6		EP6	5	R/	W	1		Endpoint		•	ole				
	5		EP	5	R/	W	1		Endpoint		•	ole				
	4		EP4	1	R/	W	1		Endpoint			ole				
	3		EPS	3	R/	W	1		Endpoint		•	ole				
	2		EP2	2	R/	W	1		Endpoint		•	ole				
	1		EP1	I	R/	W	1	TXI	Endpoint	1 Intern	upt Enab	ole				

Same description as EP7.

Bit/Field	Name	Туре	Reset	Description
0	EP0	R/W	1	TX and RX Endpoint 0 Interrupt Enable
				Value Description
				The EP0 transmit and receive interrupt is suppressed and not sent to the interrupt controller.
				An interrupt is sent to the interrupt controller when the EP0 bit in the USBTXIS register is set.

Register 6: USB Receive Interrupt Enable (USBRXIE), offset 0x008



USBRXIE is a 16-bit register that provides interrupt enable bits for the interrupts in the **USBRXIS** register. When a bit is set, the USB interrupt is asserted to the interrupt controller when the corresponding interrupt bit in the USBRXIS register is set. When a bit is cleared, the interrupt in the **USBRXIS** register is still set but the USB interrupt to the interrupt controller is not asserted. On reset, all interrupts are enabled.

OTG B / **Device**

USB Receive Interrupt Enable (USBRXIE)

Base 0x4005.0000 Offset 0x008

Туре	R/W, rese	t 0xFFFE														
	15	14	13	12	11	10	9	8	7	6	5	4	3	2	1	0
	'			rese	rved				EP7	EP6	EP5	EP4	EP3	EP2	EP1	reserved
Type Reset	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	R/W 1	R/W 1	R/W 1	R/W 1	R/W 1	R/W 1	R/W 1	RO 0
E	Bit/Field		Nam	ie	Ту	ре	Reset	Des	cription							
	15:8		reserv	/ed	R	0	0	com	patibility	with futu	ure prod	he value ucts, the dify-write	value of	a reserv		vide hould be
	7		EP7	7	R/	W	1	RXI	Endpoin	t 7 Interr	upt Enal	ole				
								Valu	ue Desc	cription						
								0		EP7 rece		rupt is si	uppresse	ed and n	ot sent t	o the
								1				the interster is se		troller w	hen the	EP7 bit
	6		EP6	6	R/	W	1		•	t 6 Interri	•	ole				
	5		EP	5	R/	W	1		•	t 5 Interription as	•	ole				
	4		EP4	1	R/	W	1			t 4 Interription as		ole				
	3		EP3	3	R/	W	1			t 3 Interription as		ole				
	2		EP2	2	R/	W	1			t 2 Interription as		ole				
	1		EP1	1	R/	W	1			t 1 Interription as		ole				
	0		reserv	ved .	R	0	0	com	patibility	with futu	ure prod	he value ucts, the dify-write	value of	a reserv		vide hould be

Register 7: USB General Interrupt Status (USBIS), offset 0x00A

Important: This register is read-sensitive. See the register description for details.

OTG A /

USBIS is an 8-bit read-only register that indicates which USB interrupts are currently active. All active interrupts are cleared when this register is read.



OTG A / Host Mode

USB General Interrupt Status (USBIS)

Base 0x4005.0000 Offset 0x00A Type RO, reset 0x00

	7	6	5	4	3	2	1	0
	VBUSERR	SESREQ	DISCON	CONN	SOF	BABBLE	RESUME	reserved
Type	RO	RO	RO	RO	RO	RO	RO	RO

Bit/Field	Name	Туре	Reset	Description
7	VBUSERR	RO	0	VBUS Error
				 Value Description No interrupt. VBUS has dropped below the VBUS Valid threshold during a session.
6	SESREQ	RO	0	SESSION REQUEST Value Description 0 No interrupt. 1 SESSION REQUEST signaling has been detected.
5	DISCON	RO	0	Session Disconnect Value Description 0 No interrupt. 1 A Device disconnect has been detected.
4	CONN	RO	0	Session Connect Value Description 0 No interrupt. 1 A Device connection has been detected.

Bit/Field	Name	Туре	Reset	Description
3	SOF	RO	0	Start of Frame
				Value Description
				0 No interrupt.
				1 A new frame has started.
2	BABBLE	RO	0	Babble Detected
				Value Description
				0 No interrupt.
				Babble has been detected. This interrupt is active only after the first SOF has been sent.
1	RESUME	RO	0	RESUME Signaling Detected
				Value Description
				0 No interrupt.
				1 RESUME signaling has been detected on the bus while the USB controller is in SUSPEND mode.
				This interrupt can only be used if the USB controller's system clock is enabled. If the user disables the clock programming, the USBDRIS , USBDRIM , and USBDRISC registers should be used.
0	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.

OTG B / Device Mode

USB General Interrupt Status (USBIS)

Base 0x4005.0000 Offset 0x00A Type RO, reset 0x00

	7	6	6 5		3	2	1	0	
	rese	rved	DISCON	reserved	SOF	RESET	RESUME	SUSPEND	
Type	RO	RO	RO	RO	RO	RO	RO	RO	
Docot	Λ	0	0	0	0	0	Λ	0	

Bit/Field	Name	Туре	Reset	Description
7:6	reserved	RO	0x0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
5	DISCON	RO	0	Session Disconnect
				Value Description
				0 No interrupt.

The device has been disconnected from the host.

Bit/Field	Name	Туре	Reset	Description
4	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
3	SOF	RO	0	Start of Frame
				Value Description
				0 No interrupt.
				1 A new frame has started.
2	RESET	RO	0	RESET Signaling Detected
				Value Description
				0 No interrupt.
				1 RESET signaling has been detected on the bus.
1	RESUME	RO	0	RESUME Signaling Detected
				Value Description
				0 No interrupt.
				1 RESUME signaling has been detected on the bus while the USB controller is in SUSPEND mode.
				This interrupt can only be used if the USB controller's system clock is enabled. If the user disables the clock programming, the USBDRIS, USBDRIM, and USBDRISC registers should be used.
0	SUSPEND	RO	0	SUSPEND Signaling Detected
				Value Description
				0 No interrupt.
				1 SUSPEND signaling has been detected on the bus.

Register 8: USB Interrupt Enable (USBIE), offset 0x00B




USBIE is an 8-bit register that provides interrupt enable bits for each of the interrupts in USBIS. At reset interrupts 1 and 2 are enabled in Device mode.

OTG B / **Device**

OTG A / Host Mode

USB Interrupt Enable (USBIE)

Base 0x4005.0000 Offset 0x00B Type R/W, reset 0x06



Bit/Field	Name	Туре	Reset	Description
7	VBUSERR	R/W	0	Enable VBUS Error Interrupt
				Value Description
				The VBUSERR interrupt is suppressed and not sent to the interrupt controller.
				An interrupt is sent to the interrupt controller when the VBUSERR bit in the USBIS register is set.
6	SESREQ	R/W	0	Enable Session Request
				Value Description
				O The SESREQ interrupt is suppressed and not sent to the interrupt controller.
				An interrupt is sent to the interrupt controller when the SESREEQ bit in the USBIS register is set.
5	DISCON	R/W	0	Enable Disconnect Interrupt
				Value Description

- The ${\tt DISCON}$ interrupt is suppressed and not sent to the interrupt 0
- An interrupt is sent to the interrupt controller when the DISCON bit in the **USBIS** register is set.

Bit/Field	Name	Туре	Reset	Description
4	CONN	R/W	0	Enable Connect Interrupt
				Value Description
				The CONN interrupt is suppressed and not sent to the interrupt controller.
				An interrupt is sent to the interrupt controller when the CONN bit in the USBIS register is set.
3	SOF	R/W	0	Enable Start-of-Frame Interrupt
				Value Description
				0 The SOF interrupt is suppressed and not sent to the interrupt controller.
				An interrupt is sent to the interrupt controller when the SOF bit in the USBIS register is set.
2	BABBLE	R/W	1	Enable Babble Interrupt
				Value Description
				O The BABBLE interrupt is suppressed and not sent to the interrupt controller.
				An interrupt is sent to the interrupt controller when the BABBLE bit in the USBIS register is set.
1	RESUME	R/W	1	Enable RESUME Interrupt
				Value Description
				O The RESUME interrupt is suppressed and not sent to the interrupt controller.
				An interrupt is sent to the interrupt controller when the RESUME bit in the USBIS register is set.
0	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.

OTG B / Device Mode

USB Interrupt Enable (USBIE)

Base 0x4005.0000 Offset 0x00B Type R/W, reset 0x06



Bit/Field	Name	Туре	Reset	Description
7:6	reserved	RO	0x0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
5	DISCON	R/W	0	Enable Disconnect Interrupt
				Value Description
				The DISCON interrupt is suppressed and not sent to the interrupt controller.
				An interrupt is sent to the interrupt controller when the DISCON bit in the USBIS register is set.
4	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
3	SOF	R/W	0	Enable Start-of-Frame Interrupt
				Value Description
				O The SOF interrupt is suppressed and not sent to the interrupt controller.
				An interrupt is sent to the interrupt controller when the SOF bit in the USBIS register is set.
2	RESET	R/W	1	Enable RESET Interrupt
				Value Description
				O The RESET interrupt is suppressed and not sent to the interrupt controller.
				An interrupt is sent to the interrupt controller when the RESET bit in the USBIS register is set.
1	RESUME	R/W	1	Enable RESUME Interrupt
				Value Description
				O The RESUME interrupt is suppressed and not sent to the interrupt controller.
				An interrupt is sent to the interrupt controller when the RESUME bit in the USBIS register is set.
0	SUSPEND	R/W	0	Enable SUSPEND Interrupt
				Value Description
				O The SUSPEND interrupt is suppressed and not sent to the interrupt controller.
				1 An interrupt is sent to the interrupt controller when the SUSPEND bit in the USBIS register is set.

Register 9: USB Frame Value (USBFRAME), offset 0x00C

OTG A /

USBFRAME is a 16-bit read-only register that holds the last received frame number.

Host

USB Frame Value (USBFRAME)

Base 0x4005.0000 Offset 0x00C Type RO, reset 0x0000

OTG B / **Device**

	15	14	13	12	11	10	9	8	7	6	5	4	3	2	1	0
			reserved		i			1	ı ı	1	FRAME		ı		1	_
Туре	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO
Reset	Λ	Λ	Λ	Λ	Λ	Λ	Λ	Λ	Λ	0	Λ	Λ	Λ	Λ	Λ	Λ

Bit/Field	Name	Туре	Reset	Description
15:11	reserved	RO	0x0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
10:0	FRAME	RO	0x000	Frame Number

Register 10: USB Endpoint Index (USBEPIDX), offset 0x00E



Each endpoint's buffer can be accessed by configuring a FIFO size and starting address. The **USBEPIDX** 8-bit register is used with the **USBTXFIFOSZ**, **USBRXFIFOSZ**, **USBTXFIFOADD**, and **USBRXFIFOADD** registers.

OTG B / Device

USB Endpoint Index (USBEPIDX)

Base 0x4005.0000 Offset 0x00E Type R/W, reset 0x00



Bit/Field	Name	Type	Reset	Description
Ditricia	Name	Турс	110001	Beschiption
7:4	reserved	RO	0x0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
3:0	EPIDX	R/W	0x0	Endpoint Index

This bit field configures which endpoint is accessed when reading or writing to one of the USB controller's indexed registers. A value of 0x0 corresponds to Endpoint 0 and a value of 0x7 corresponds to Endpoint 7.

Register 11: USB Test Mode (USBTEST), offset 0x00F



USBTEST is an 8-bit register that is primarily used to put the USB controller into one of the four test modes for operation described in the USB 2.0 Specification, in response to a SET FEATURE: USBTESTMODE command. This register is not used in normal operation.


OTG B / **Device**

Note: Only one of these bits should be set at any time.

OTG A / Host Mode

USB Test Mode (USBTEST)

Base 0x4005.0000 Offset 0x00F Type R/W, reset 0x00



Bit/Field	Name	Type	Reset	Description
7	FORCEH	R/W	0	Force Host Mode
				Value Description

0

No effect.

Forces the USB controller to enter Host mode when the 1 SESSION bit is set, regardless of whether the USB controller is connected to any peripheral. The state of the USBODP and USBODM signals is ignored. The USB controller then remains in Host mode until the SESSION bit is cleared, even if a Device is

disconnected. If the FORCEH bit remains set, the USB controller re-enters Host mode the next time the SESSION bit is set.

While in this mode, status of the bus connection may be read using the DEV bit of the USBDEVCTL register. The operating speed is determined from the FORCEFS bit.

6 **FIFOACC** R/W1S Λ FIFO Access

Value Description

- 0 No effect.
- 1 Transfers the packet in the endpoint 0 transmit FIFO to the endpoint 0 receive FIFO.

This bit is cleared automatically.

5 **FORCEFS** R/W 0 Force Full-Speed Mode

Value Description

- 0 The USB controller operates at Low Speed.
- Forces the USB controller into Full-Speed mode upon receiving a USB RESET.

Bit/Field	Name	Туре	Reset	Description
4:0	reserved	RO	0x0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.

OTG B / Device Mode

USB Test Mode (USBTEST)

Base 0x4005.0000 Offset 0x00F Type R/W, reset 0x00

	7	6	5	4	3	2	1	0	
	reserved	FIFOACC	FORCEFS		1	reserved		1	
Type	RO	R/W1S	R/W	RO	RO	RO	RO	RO	
Reset	Λ	0	0	Ω	0	0	0	Λ	

Bit/Field	Name	Туре	Reset	Description
7	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
6	FIFOACC	R/W1S	0	FIFO Access
				Value Description
				1 Transfers the packet in the endpoint 0 transmit FIFO to the endpoint 0 receive FIFO.
				0 No effect.
				This bit is cleared automatically.
5	FORCEFS	R/W	0	Force Full-Speed Mode
				Value Description
				0 The USB controller operates at Low Speed.
				1 Forces the USB controller into Full-Speed mode upon receiving a USB RESET.
4:0	reserved	RO	0x0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.

Register 12: USB FIFO Endpoint 0 (USBFIFO0), offset 0x020

Register 13: USB FIFO Endpoint 1 (USBFIFO1), offset 0x024

Register 14: USB FIFO Endpoint 2 (USBFIFO2), offset 0x028

Register 15: USB FIFO Endpoint 3 (USBFIFO3), offset 0x02C

Register 16: USB FIFO Endpoint 4 (USBFIFO4), offset 0x030

Register 17: USB FIFO Endpoint 5 (USBFIFO5), offset 0x034

Register 18: USB FIFO Endpoint 6 (USBFIFO6), offset 0x038

Register 19: USB FIFO Endpoint 7 (USBFIFO7), offset 0x03C

Important: This register is read-sensitive. See the register description for details.

OTG A / Host These 32-bit registers provide an address for CPU access to the FIFOs for each endpoint. Writing to these addresses loads data into the Transmit FIFO for the corresponding endpoint. Reading from these addresses unloads data from the Receive FIFO for the corresponding endpoint.

OTG B / Device Transfers to and from FIFOs may be 8-bit, 16-bit or 32-bit as required, and any combination of accesses is allowed provided the data accessed is contiguous. All transfers associated with one packet must be of the same width so that the data is consistently byte-, halfword- or word-aligned. However, the last transfer may contain fewer bytes than the previous transfers in order to complete an odd-byte or odd-word transfer.


Depending on the size of the FIFO and the expected maximum packet size, the FIFOs support either single-packet or double-packet buffering (see the section called "Single-Packet Buffering" on page 1108). Burst writing of multiple packets is not supported as flags must be set after each packet is written.

Following a STALL response or a transmit error on endpoint 1–7, the associated FIFO is completely flushed.

USB FIFO Endpoint n (USBFIFOn)

Base 0x4005.0000 Offset 0x020

Type R/W, reset 0x0000.0000



Writing to this register loads the data into the Transmit FIFO and reading unloads data from the Receive FIFO.

Register 20: USB Device Control (USBDEVCTL), offset 0x060



USBDEVCTL is an 8-bit register used for controlling and monitoring the USB VBUS line. If the PHY is suspended, no PHY clock is received and the VBUS is not sampled. In addition, in Host mode, **USBDEVCTL** provides the status information for the current operating mode (Host or Device) of the USB controller. If the USB controller is in Host mode, this register also indicates if a full- or low-speed Device has been connected.

USB Device Control (USBDEVCTL)

Base 0x4005.0000 Offset 0x060 Type R/W, reset 0x80

	7	6	5	4	3	2	1	0
	DEV	FSDEV	LSDEV	VB	US	HOST	HOSTREQ	SESSION
Type	RO	RO	RO	RO	RO	RO	R/W	R/W
Reset	1	0	0	0	0	0	0	0

Bit/Field	Name	Туре	Reset	Description
7	DEV	RO	1	Device Mode
				Value Description
				0 The USB controller is operating on the OTG A side of the cable.
				1 The USB controller is operating on the OTG B side of the cable.
				Note: This value is only valid while a session is in progress.
6	FSDEV	RO	0	Full-Speed Device Detected
				Value Description
				0 A full-speed Device has not been detected on the port.
				1 A full-speed Device has been detected on the port.
5	LSDEV	RO	0	Low-Speed Device Detected
				Value Description
				O A low-speed Device has not been detected on the port.
				1 A low-speed Device has been detected on the port.
4:3	VBUS	RO	0x0	VBUS Level
				Value Description
				0x0 Below SessionEnd
				VBUS is detected as under 0.5 V.
				0x1 Above SessionEnd, below AValid
				VBUS is detected as above 0.5 V and under 1.5 V.
				0x2 Above AValid, below VBUSValid
				VBUS is detected as above 1.5 V and below 4.75 V.
				0x3 Above VBUSValid
				VBUS is detected as above 4.75 V.

Bit/Field	Name	Type	Reset	Description
2	HOST	RO	0	Host Mode
				Value Description O The USB controller is acting as a Device.
				1 The USB controller is acting as a Host.
				Note: This value is only valid while a session is in progress.
1	HOSTREQ	R/W	0	Host Request
				Value Description
				0 No effect.
				1 Initiates the Host Negotiation when SUSPEND mode is entered.
				This bit is cleared when Host Negotiation is completed.
0	SESSION	R/W	0	Session Start/End
				When operating as an OTG A device:
				Value Description
				0 When cleared by software, this bit ends a session.
				1 When set by software, this bit starts a session.

Value Description

When operating as an OTG B device:

- The USB controller has ended a session. When the USB controller is in SUSPEND mode, this bit may be cleared by software to perform a software disconnect.
- 1 The USB controller has started a session. When set by software, the Session Request Protocol is initiated.

Note: Clearing this bit when the USB controller is not suspended results in undefined behavior.

Register 21: USB Transmit Dynamic FIFO Sizing (USBTXFIFOSZ), offset 0x062 Register 22: USB Receive Dynamic FIFO Sizing (USBRXFIFOSZ), offset 0x063



These 8-bit registers allow the selected TX/RX endpoint FIFOs to be dynamically sized. **USBEPIDX** is used to configure each transmit endpoint's FIFO size.

USB Dynamic FIFO Sizing (USBnXFIFOSZ)

OTG B /
Device

Base 0x4005.0000 Offset 0x062 Type R/W, reset 0x00

	7	6	5	4	3	2	1	0
		reserved				SI	ZE	
Type	RO	RO	RO	R/W	R/W	R/W	R/W	R/W
Reset	0	0	0	0	0	0	0	0

Bit/Field	Name	Туре	Reset	Description
7:5	reserved	RO	0x0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
4	DPB	R/W	0	Double Packet Buffer Support
				Value Description
				Only single-packet buffering is supported.
				1 Double-packet buffering is supported.
3:0	SIZE	R/W	0x0	Max Packet Size

Maximum packet size to be allowed.

If ${\tt DPB}$ = 0, the FIFO also is this size; if ${\tt DPB}$ = 1, the FIFO is twice this size.

Value	Packet Size (Bytes)
0x0	8
0x1	16
0x2	32
0x3	64
0x4	128
0x5	256
0x6	512
0x7	1024
8x0	2048
0x9-0xF	Reserved


Register 23: USB Transmit FIFO Start Address (USBTXFIFOADD), offset 0x064 Register 24: USB Receive FIFO Start Address (USBRXFIFOADD), offset 0x066



USBTXFIFOADD and **USBRXFIFOADD** are 16-bit registers that control the start address of the selected transmit and receive endpoint FIFOs.

USB Transmit FIFO Start Address (USBnXFIFOADD)

OTG B / Device Base 0x4005.0000 Offset 0x064 Type R/W, reset 0x0000



Bit/Field	Name	Туре	Reset	Description
15:9	reserved	RO	0x00	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
8:0	ADDR	R/W	0x00	Transmit/Receive Start Address Start address of the endpoint FIFO.

Value	Start Address
0x0	0
0x1	8
0x2	16
0x3	24
0x4	32
0x5	40
0x6	48
0x7	56
0x8	64
0x1FF	4095

Register 25: USB Connect Timing (USBCONTIM), offset 0x07A

OTG A /

This 8-bit configuration register specifies connection and negotiation delays.

Host

USB Connect Timing (USBCONTIM)
Base 0x4005.0000

Offset 0x07A
Type R/W, reset 0x5C

OTG B / Device

	7	6	5	4	3	2	1	0
	WTCON			WTID				
Type	R/W	R/W	R/W	R/W	R/W	R/W	R/W	R/W
Reset	Λ	1	Λ	1	1	1	Λ	Λ

Bit/Field	Name	Type	Reset	Description
7:4	WTCON	R/W	0x5	Connect Wait
				This field configures the wait required to allow for the user's connect/disconnect filter, in units of 533.3 ns. The default corresponds to 2.667 μs .
3:0	WTID	R/W	0xC	Wait ID This field configures the delay required from the anable of the ID

This field configures the delay required from the enable of the ID detection to when the ID value is valid, in units of 4.369 ms. The default corresponds to 52.43 ms.


Register 26: USB OTG VBUS Pulse Timing (USBVPLEN), offset 0x07B

OTG

This 8-bit configuration register specifies the duration of the VBUS pulsing charge.

USB OTG VBUS Pulse Timing (USBVPLEN)

Base 0x4005.0000 Offset 0x07B Type R/W, reset 0x3C



Bit/Field	Name	Type	Reset	Description
7:0	VPLEN	R/W	0x3C	VBUS Pulse Length

This field configures the duration of the VBUS pulsing charge in units of 546.1 μs . The default corresponds to 32.77 ms.

Register 27: USB Full-Speed Last Transaction to End of Frame Timing (USBFSEOF), offset 0x07D


OTG A /

This 8-bit configuration register specifies the minimum time gap allowed between the start of the last transaction and the EOF for full-speed transactions.

USB Full-Speed Last Transaction to End of Frame Timing (USBFSEOF)

OTG B /
Device





Bit/Field	Name	Type	Reset	Description
7:0	FSEOFG	R/W	0x77	Full-Speed End-of-Frame Gap

This field is used during full-speed transactions to configure the gap between the last transaction and the End-of-Frame (EOF), in units of 533.3 ns. The default corresponds to 63.46 μs .

Register 28: USB Low-Speed Last Transaction to End of Frame Timing (USBLSEOF), offset 0x07E


OTG A /

This 8-bit configuration register specifies the minimum time gap that is to be allowed between the start of the last transaction and the EOF for low-speed transactions.

USB Low-Speed Last Transaction to End of Frame Timing (USBLSEOF)

OTG B /
Device





Bit/Field Name Type Reset Description

7:0 LSEOFG R/W 0x72 Low-Speed End-of-Frame Gap

This field is used during low-speed transactions to set the gap between the last transaction and the End-of-Frame (EOF), in units of 1.067 μ s. The default corresponds to 121.6 μ s.

Register 29: USB Transmit Functional Address Endpoint 0 (USBTXFUNCADDR0), offset 0x080

Register 30: USB Transmit Functional Address Endpoint 1 (USBTXFUNCADDR1), offset 0x088

Register 31: USB Transmit Functional Address Endpoint 2 (USBTXFUNCADDR2), offset 0x090

Register 32: USB Transmit Functional Address Endpoint 3 (USBTXFUNCADDR3), offset 0x098

Register 33: USB Transmit Functional Address Endpoint 4 (USBTXFUNCADDR4), offset 0x0A0

Register 34: USB Transmit Functional Address Endpoint 5 (USBTXFUNCADDR5), offset 0x0A8

Register 35: USB Transmit Functional Address Endpoint 6 (USBTXFUNCADDR6), offset 0x0B0

Register 36: USB Transmit Functional Address Endpoint 7 (USBTXFUNCADDR7), offset 0x0B8




USBTXFUNCADDRn is an 8-bit read/write register that records the address of the target function to be accessed through the associated endpoint (EPn). **USBTXFUNCADDRn** must be defined for each transmit endpoint that is used.

Note: USBTXFUNCADDR0 is used for both receive and transmit for endpoint 0.

USB Transmit Functional Address Endpoint n (USBTXFUNCADDRn)

Base 0x4005.0000 Offset 0x080 Type R/W, reset 0x00



Bit/Field	Name	Type	Reset	Description
7	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
6:0	ADDR	R/W	0x00	Device Address Specifies the USB bus address for the target Device.

February 20, 2013 1155

Register 37: USB Transmit Hub Address Endpoint 0 (USBTXHUBADDR0), offset 0x082

Register 38: USB Transmit Hub Address Endpoint 1 (USBTXHUBADDR1), offset 0x08A

Register 39: USB Transmit Hub Address Endpoint 2 (USBTXHUBADDR2), offset 0x092

Register 40: USB Transmit Hub Address Endpoint 3 (USBTXHUBADDR3), offset 0x09A

Register 41: USB Transmit Hub Address Endpoint 4 (USBTXHUBADDR4), offset 0x0A2

Register 42: USB Transmit Hub Address Endpoint 5 (USBTXHUBADDR5), offset 0x0AA

Register 43: USB Transmit Hub Address Endpoint 6 (USBTXHUBADDR6), offset 0x0B2

Register 44: USB Transmit Hub Address Endpoint 7 (USBTXHUBADDR7), offset 0x0BA




USBTXHUBADDRn is an 8-bit read/write register that, like **USBTXHUBPORTn**, only must be written when a USB Device is connected to transmit endpoint EPn via a USB 2.0 hub. This register records the address of the USB 2.0 hub through which the target associated with the endpoint is accessed.

Note: USBTXHUBADDR0 is used for both receive and transmit for endpoint 0.

USB Transmit Hub Address Endpoint n (USBTXHUBADDRn)

Base 0x4005.0000 Offset 0x082 Type R/W, reset 0x00



Bit/Field	Name	Туре	Reset	Description
7	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
6:0	ADDR	R/W	0x00	Hub Address

This field specifies the USB bus address for the USB 2.0 hub.

1156 February 20, 2013

Register 45: USB Transmit Hub Port Endpoint 0 (USBTXHUBPORT0), offset 0x083

Register 46: USB Transmit Hub Port Endpoint 1 (USBTXHUBPORT1), offset 0x08B

Register 47: USB Transmit Hub Port Endpoint 2 (USBTXHUBPORT2), offset 0x093

Register 48: USB Transmit Hub Port Endpoint 3 (USBTXHUBPORT3), offset 0x09B

Register 49: USB Transmit Hub Port Endpoint 4 (USBTXHUBPORT4), offset 0x0A3

Register 50: USB Transmit Hub Port Endpoint 5 (USBTXHUBPORT5), offset 0x0AB

Register 51: USB Transmit Hub Port Endpoint 6 (USBTXHUBPORT6), offset 0x0B3

Register 52: USB Transmit Hub Port Endpoint 7 (USBTXHUBPORT7), offset 0x0BB




USBTXHUBPORTn is an 8-bit read/write register that, like **USBTXHUBADDRn**, only must be written when a full- or low-speed Device is connected to transmit endpoint EPn via a USB 2.0 hub. This register records the port of the USB 2.0 hub through which the target associated with the endpoint is accessed.

Note: USBTXHUBPORT0 is used for both receive and transmit for endpoint 0.

USB Transmit Hub Port Endpoint n (USBTXHUBPORTn)

Base 0x4005.0000 Offset 0x083 Type R/W, reset 0x00



Bit/Field	Name	Type	Reset	Description
7	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
6:0	PORT	R/W	0x00	Hub Port

This field specifies the USB hub port number.

Register 53: USB Receive Functional Address Endpoint 1 (USBRXFUNCADDR1), offset 0x08C

Register 54: USB Receive Functional Address Endpoint 2 (USBRXFUNCADDR2), offset 0x094

Register 55: USB Receive Functional Address Endpoint 3 (USBRXFUNCADDR3), offset 0x09C

Register 56: USB Receive Functional Address Endpoint 4 (USBRXFUNCADDR4), offset 0x0A4

Register 57: USB Receive Functional Address Endpoint 5 (USBRXFUNCADDR5), offset 0x0AC

Register 58: USB Receive Functional Address Endpoint 6 (USBRXFUNCADDR6), offset 0x0B4

Register 59: USB Receive Functional Address Endpoint 7 (USBRXFUNCADDR7), offset 0x0BC




USBRXFUNCADDRn is an 8-bit read/write register that records the address of the target function accessed through the associated endpoint (EPn). **USBRXFUNCADDRn** must be defined for each receive endpoint that is used.

Note: USBTXFUNCADDR0 is used for both receive and transmit for endpoint 0.

USB Receive Functional Address Endpoint n (USBRXFUNCADDRn)

Base 0x4005.0000 Offset 0x08C Type R/W, reset 0x00



Bit/Field	Name	Type	Reset	Description
7	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
6:0	ADDR	R/W	0x00	Device Address

This field specifies the USB bus address for the target Device.

 Register 60: USB Receive Hub Address Endpoint 1 (USBRXHUBADDR1), offset 0x08E

Register 61: USB Receive Hub Address Endpoint 2 (USBRXHUBADDR2), offset 0x096

Register 62: USB Receive Hub Address Endpoint 3 (USBRXHUBADDR3), offset 0x09E

Register 63: USB Receive Hub Address Endpoint 4 (USBRXHUBADDR4), offset 0x0A6

Register 64: USB Receive Hub Address Endpoint 5 (USBRXHUBADDR5), offset 0x0AE

Register 65: USB Receive Hub Address Endpoint 6 (USBRXHUBADDR6), offset 0x0B6

Register 66: USB Receive Hub Address Endpoint 7 (USBRXHUBADDR7), offset 0x0BE




USBRXHUBADDRn is an 8-bit read/write register that, like **USBRXHUBPORTn**, only must be written when a full- or low-speed Device is connected to receive endpoint EPn via a USB 2.0 hub. This register records the address of the USB 2.0 hub through which the target associated with the endpoint is accessed.

Note: USBTXHUBADDR0 is used for both receive and transmit for endpoint 0.

USB Receive Hub Address Endpoint n (USBRXHUBADDRn)

Base 0x4005.0000 Offset 0x08E Type R/W, reset 0x00



Bit/Field	Name	Type	Reset	Description
7	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
6:0	ADDR	R/W	0x00	Hub Address

This field specifies the USB bus address for the USB 2.0 hub.

Register 67: USB Receive Hub Port Endpoint 1 (USBRXHUBPORT1), offset 0x08F

Register 68: USB Receive Hub Port Endpoint 2 (USBRXHUBPORT2), offset 0x097

Register 69: USB Receive Hub Port Endpoint 3 (USBRXHUBPORT3), offset 0x09F

Register 70: USB Receive Hub Port Endpoint 4 (USBRXHUBPORT4), offset 0x0A7

Register 71: USB Receive Hub Port Endpoint 5 (USBRXHUBPORT5), offset 0x0AF

Register 72: USB Receive Hub Port Endpoint 6 (USBRXHUBPORT6), offset 0x0B7

Register 73: USB Receive Hub Port Endpoint 7 (USBRXHUBPORT7), offset 0x0BF




USBRXHUBPORTn is an 8-bit read/write register that, like **USBRXHUBADDRn**, only must be written when a full- or low-speed Device is connected to receive endpoint EPn via a USB 2.0 hub. This register records the port of the USB 2.0 hub through which the target associated with the endpoint is accessed.

Note: USBTXHUBPORT0 is used for both receive and transmit for endpoint 0.

USB Receive Hub Port Endpoint n (USBRXHUBPORTn)

Base 0x4005.0000 Offset 0x08F Type R/W, reset 0x00



Bit/Field	Name	Type	Reset	Description
7	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
6:0	PORT	R/W	0x00	Hub Port

This field specifies the USB hub port number.

Register 74: USB Maximum Transmit Data Endpoint 1 (USBTXMAXP1), offset 0x110

Register 75: USB Maximum Transmit Data Endpoint 2 (USBTXMAXP2), offset 0x120

Register 76: USB Maximum Transmit Data Endpoint 3 (USBTXMAXP3), offset 0x130

Register 77: USB Maximum Transmit Data Endpoint 4 (USBTXMAXP4), offset 0x140

Register 78: USB Maximum Transmit Data Endpoint 5 (USBTXMAXP5), offset 0x150

Register 79: USB Maximum Transmit Data Endpoint 6 (USBTXMAXP6), offset 0x160

Register 80: USB Maximum Transmit Data Endpoint 7 (USBTXMAXP7), offset 0x170

OTG A / Host The **USBTXMAXPn** 16-bit register defines the maximum amount of data that can be transferred through the transmit endpoint in a single operation.

OTG B /

Bits 10:0 define (in bytes) the maximum payload transmitted in a single transaction. The value set can be up to 1024 bytes but is subject to the constraints placed by the *USB Specification* on packet sizes for bulk, interrupt and isochronous transfers in full-speed operation.


The total amount of data represented by the value written to this register must not exceed the FIFO size for the transmit endpoint, and must not exceed half the FIFO size if double-buffering is required.

If this register is changed after packets have been sent from the endpoint, the transmit endpoint FIFO must be completely flushed (using the FLUSH bit in **USBTXCSRLn**) after writing the new value to this register.

Note: USBTXMAXPn must be set to an even number of bytes for proper interrupt generation in µDMA Basic Mode.

USB Maximum Transmit Data Endpoint n (USBTXMAXPn)

Base 0x4005.0000 Offset 0x110 Type R/W, reset 0x0000



Register 81: USB Control and Status Endpoint 0 Low (USBCSRL0), offset 0x102




USBCSRL0 is an 8-bit register that provides control and status bits for endpoint 0.

OTG B /

OTG A / Host Mode

USB Control and Status Endpoint 0 Low (USBCSRL0)

Base 0x4005.0000 Offset 0x102 Type W1C, reset 0x00



Bit/Field	Name	Туре	Reset	Description
7	NAKTO	R/W	0	NAK Timeout
				Value Description 0 No timeout.
				Indicates that endpoint 0 is halted following the receipt of NAK responses for longer than the time set by the USBNAKLMT register.
				Software must clear this bit to allow the endpoint to continue.
6	STATUS	R/W	0	STATUS Packet
				Value Description
				0 No transaction.
				1 Initiates a STATUS stage transaction. This bit must be set at the same time as the TXRDY or REQPKT bit is set.
				Setting this bit ensures that the DT bit is set in the USBCSRH0 register so that a DATA1 packet is used for the STATUS stage transaction.
				This bit is automatically cleared when the STATUS stage is over.
5	REQPKT	R/W	0	Request Packet
				Value Description
				0 No request.
				1 Requests an IN transaction.
				This bit is cleared when the RXRDY bit is set.

Bit/Field	Name	Туре	Reset	Description
4	ERROR	R/W	0	Error
				Value Description
				0 No error.
				Three attempts have been made to perform a transaction with no response from the peripheral. The EPO bit in the USBTXIS register is also set in this situation.
				Software must clear this bit.
3	SETUP	R/W	0	Setup Packet
				Value Description
				0 Sends an OUT token.
				Sends a SETUP token instead of an OUT token for the transaction. This bit should be set at the same time as the TXRDY bit is set.
				Setting this bit always clears the ${\tt DT}$ bit in the $\textbf{USBCSRH0}$ register to send a DATA0 packet.
2	STALLED	R/W	0	Endpoint Stalled
				Value Description
				0 No handshake has been received.
				1 A STALL handshake has been received.
				Software must clear this bit.
1	TXRDY	R/W	0	Transmit Packet Ready
				Value Description
				0 No transmit packet is ready.
				Software sets this bit after loading a data packet into the TX FIFO. The EPO bit in the USBTXIS register is also set in this situation.
				If both the TXRDY and SETUP bits are set, a setup packet is sent. If just TXRDY is set, an OUT packet is sent.
				This bit is cleared automatically when the data packet has been transmitted.
0	RXRDY	R/W	0	Receive Packet Ready
				Value Description
				0 No received packet has been received.
				Indicates that a data packet has been received in the RX FIFO. The EPO bit in the USBTXIS register is also set in this situation.


February 20, 2013 1163

Software must clear this bit after the packet has been read from the FIFO to acknowledge that the data has been read from the FIFO.

OTG B / Device Mode

USB Control and Status Endpoint 0 Low (USBCSRL0)

Base 0x4005.0000 Offset 0x102 Type W1C, reset 0x00



Bit/Field	Name	Type	Reset	Description
7	SETENDC	W1C	0	Setup End Clear
				Writing a 1 to this bit clears the SETEND bit.
6	RXRDYC	W1C	0	RXRDY Clear
				Writing a 1 to this bit clears the RXRDY bit.
5	STALL	R/W	0	Send Stall
				Value Description
				0 No effect.
				1 Terminates the current transaction and transmits the STALL handshake.
				This bit is cleared automatically after the STALL handshake is transmitted.
4	SETEND	RO	0	Setup End
				Value Description
				O A control transaction has not ended or ended after the DATAEND bit was set.
				A control transaction has ended before the DATAEND bit has been set. The EPO bit in the USBTXIS register is also set in this situation.
				This bit is cleared by writing a 1 to the SETENDC bit.
3	DATAEND	R/W	0	Data End
				Value Description
				0 No effect.
				1 Set this bit in the following situations:
				■ When setting TXRDY for the last data packet
				 When clearing RXRDY after unloading the last data packet

This bit is cleared automatically.

■ When setting TXRDY for a zero-length data packet

Bit/Field	Name	Туре	Reset	Description
2	STALLED	R/W	0	Endpoint Stalled
				Value Description O A STALL handshake has not been transmitted. 1 A STALL handshake has been transmitted. Software must clear this bit.
1	TXRDY	R/W	0	Transmit Packet Ready Value Description 0 No transmit packet is ready.
				 Software sets this bit after loading an IN data packet into the TX FIFO. The EPO bit in the USBTXIS register is also set in this situation. This bit is cleared automatically when the data packet has been transmitted.
0	RXRDY	RO	0	Packet Ready Value Description No data packet has been received. A data packet has been received. The EPO bit in the USBTXIS

This bit is cleared by writing a 1 to the ${\tt RXRDYC}$ bit.

register is also set in this situation.

February 20, 2013 1165

Register 82: USB Control and Status Endpoint 0 High (USBCSRH0), offset 0x103



USBSR0H is an 8-bit register that provides control and status bits for endpoint 0.



OTG A / Host Mode

USB Control and Status Endpoint 0 High (USBCSRH0)

Base 0x4005.0000 Offset 0x103 Type W1C, reset 0x00



Bit/Field	Name	Туре	Reset	Description
7:3	reserved	RO	0x0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
2	DTWE	R/W	0	 Data Toggle Write Enable Value Description The DT bit cannot be written. Enables the current state of the endpoint 0 data toggle to be written (see DT bit). This bit is automatically cleared once the new value is written.
1	DT	R/W	0	Data Toggle When read, this bit indicates the current state of the endpoint 0 data toggle.

If DTWE is set, this bit may be written with the required setting of the data toggle. If DTWE is Low, this bit cannot be written. Care should be taken when writing to this bit as it should only be changed to RESET USB endpoint 0.

Bit/Field	Name	Type	Reset	Description
0	FLUSH	R/W	0	Flush FIFO

Value Description

- 0 No effect.
- Flushes the next packet to be transmitted/read from the endpoint 0 FIFO. The FIFO pointer is reset and the TXRDY/RXRDY bit is cleared.


This bit is automatically cleared after the flush is performed.

Important: This bit should only be set when TXRDY is clear and RXRDY is set. At other times, it may cause data to be corrupted.

OTG B / Device Mode

USB Control and Status Endpoint 0 High (USBCSRH0)

Base 0x4005.0000 Offset 0x103 Type W1C, reset 0x00



Bit/Field	Name	Type	Reset	Description
7:1	reserved	RO	0x00	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
0	FLUSH	R/W	0	Flush FIFO

Value Description

- 0 No effect.
- Flushes the next packet to be transmitted/read from the endpoint 0 FIFO. The FIFO pointer is reset and the TXRDY/RXRDY bit is cleared.

This bit is automatically cleared after the flush is performed.

Important: This bit should only be set when TXRDY is clear and RXRDY is set. At other times, it may cause data to be corrupted.

Register 83: USB Receive Byte Count Endpoint 0 (USBCOUNT0), offset 0x108




USBCOUNT0 is an 8-bit read-only register that indicates the number of received data bytes in the endpoint 0 FIFO. The value returned changes as the contents of the FIFO change and is only valid while the RXRDY bit is set.

OTG B /
Device

USB Receive Byte Count Endpoint 0 (USBCOUNT0)

Base 0x4005.0000 Offset 0x108 Type RO, reset 0x00



Bit/Field	Name	Туре	Reset	Description
7	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
6:0	COUNT	RO	0x00	FIFO Count

 ${\tt COUNT}$ is a read-only value that indicates the number of received data bytes in the endpoint 0 FIFO.

Register 84: USB Type Endpoint 0 (USBTYPE0), offset 0x10A



This is an 8-bit register that must be written with the operating speed of the targeted Device being communicated with using endpoint 0.


USB Type Endpoint 0 (USBTYPE0)

Base 0x4005.0000

Name

Offset 0x10A Type R/W, reset 0x00

Bit/Field



Type

Reset

		• • •		•	
7:6	SPEED	R/W	0x0	Operating Speed	
				This field specifies the operating speed of the target Device. If see the target is assumed to have the same connection speed as the controller.	
				Value Description	
				0x0 - 0x1 Reserved	
				0x2 Full	
				0x3 Low	
5:0	reserved	RO	0x0	Software should not rely on the value of a reserved bit. To provi	ride

Description

compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.

Register 85: USB NAK Limit (USBNAKLMT), offset 0x10B




USBNAKLMT is an 8-bit register that sets the number of frames after which endpoint 0 should time out on receiving a stream of NAK responses. (Equivalent settings for other endpoints can be made through their **USBTXINTERVALn** and **USBRXINTERVALn** registers.)

The number of frames selected is $2^{(m-1)}$ (where m is the value set in the register, with valid values of 2–16). If the Host receives NAK responses from the target for more frames than the number represented by the limit set in this register, the endpoint is halted.

Note: A value of 0 or 1 disables the NAK timeout function.

USB NAK Limit (USBNAKLMT)

Base 0x4005.0000 Offset 0x10B Type R/W, reset 0x00



Bit/Field	Name	Type	Reset	Description
7:5	reserved	RO	0x0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
4:0	NAKLMT	R/W	0x0	EP0 NAK Limit

This field specifies the number of frames after receiving a stream of NAK responses.

Register 86: USB Transmit Control and Status Endpoint 1 Low (USBTXCSRL1), offset 0x112

Register 87: USB Transmit Control and Status Endpoint 2 Low (USBTXCSRL2), offset 0x122

Register 88: USB Transmit Control and Status Endpoint 3 Low (USBTXCSRL3), offset 0x132

Register 89: USB Transmit Control and Status Endpoint 4 Low (USBTXCSRL4), offset 0x142

Register 90: USB Transmit Control and Status Endpoint 5 Low (USBTXCSRL5), offset 0x152

Register 91: USB Transmit Control and Status Endpoint 6 Low (USBTXCSRL6), offset 0x162

Register 92: USB Transmit Control and Status Endpoint 7 Low (USBTXCSRL7), offset 0x172




USBTXCSRLn is an 8-bit register that provides control and status bits for transfers through the currently selected transmit endpoint.



OTG A / Host Mode

USB Transmit Control and Status Endpoint n Low (USBTXCSRLn)

Base 0x4005.0000 Offset 0x112 Type R/W, reset 0x00



Bit/Field	Name	Type	Reset	Description
7	NAKTO	R/W	0	NAK Timeout

Value Description

0 No timeout.

Bulk endpoints only: Indicates that the transmit endpoint is halted following the receipt of NAK responses for longer than the time set by the NAKLMT field in the USBTXINTERVALn register. Software must clear this bit to allow the endpoint to continue.

Bit/Field	Name	Туре	Reset	Description
6	CLRDT	R/W	0	Clear Data Toggle Writing a 1 to this bit clears the DT bit in the USBTXCSRHn register.
5	STALLED	R/W	0	Endpoint Stalled
				Value Description
				0 A STALL handshake has not been received.
				Indicates that a STALL handshake has been received. When this bit is set, any μDMA request that is in progress is stopped, the FIFO is completely flushed, and the TXRDY bit is cleared.
				Software must clear this bit.
4	SETUP	R/W	0	Setup Packet
				Value Description
				0 No SETUP token is sent.
				Sends a SETUP token instead of an OUT token for the transaction. This bit should be set at the same time as the TXRDY bit is set.
				Note: Setting this bit also clears the DT bit in the USBTXCSRHn register.
3	FLUSH	R/W	0	Flush FIFO
				Value Description
				0 No effect.
				1 Flushes the latest packet from the endpoint transmit FIFO. The FIFO pointer is reset and the TXRDY bit is cleared. The EPn bit in the USBTXIS register is also set in this situation.
				This bit may be set simultaneously with the TXRDY bit to abort the packet that is currently being loaded into the FIFO. Note that if the FIFO is double-buffered, FLUSH may have to be set twice to completely clear the FIFO.
				Important: This bit should only be set when the TXRDY bit is clear. At other times, it may cause data to be corrupted.
2	ERROR	R/W	0	Error
				Value Description
				0 No error.
				Three attempts have been made to send a packet and no handshake packet has been received. The TXRDY bit is cleared, the EPn bit in the USBTXIS register is set, and the FIFO is completely flushed in this situation.
				Software must clear this bit.

Note:

This is valid only when the endpoint is operating in Bulk or Interrupt mode.

Bit/Field	Name	Type	Reset	Description
1	FIFONE	R/W	0	FIFO Not Empty
				Value Description The FIFO is empty. At least one packet is in the transmit FIFO.
0	TXRDY	R/W	0	Transmit Packet Ready

Value Description

- 0 No transmit packet is ready.
- Software sets this bit after loading a data packet into the TX FIFO


This bit is cleared automatically when a data packet has been transmitted. The \mathtt{EPn} bit in the **USBTXIS** register is also set at this point. \mathtt{TXRDY} is also automatically cleared prior to loading a second packet into a double-buffered FIFO.

OTG B / Device Mode

USB Transmit Control and Status Endpoint n Low (USBTXCSRLn)

Base 0x4005.0000 Offset 0x112 Type R/W, reset 0x00

5



STALLED

R/W

0

Bit/Field	Name	Туре	Reset	Description
7	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
6	CLRDT	R/W	0	Clear Data Toggle Writing a 1 to this bit clears the DT bit in the USBTXCSRHn register.

Value Description

Endpoint Stalled

- 0 A STALL handshake has not been transmitted.
- 1 A STALL handshake has been transmitted. The FIFO is flushed and the TXRDY bit is cleared.

Software must clear this bit.

Bit/Field	Name	Туре	Reset	Description
4	STALL	R/W	0	Send STALL
				Value Description 0 No effect. 1 Issues a STALL handshake to an IN token. Software clears this bit to terminate the STALL condition. Note: This bit has no effect in isochronous transfers.
2	FLUSH	R/W	0	Flush FIFO
3	FLUSH	R/W	U	Value Description No effect. Flushes the latest packet from the endpoint transmit FIFO. The FIFO pointer is reset and the TXRDY bit is cleared. The EPn bit in the USBTXIS register is also set in this situation. This bit may be set simultaneously with the TXRDY bit to abort the packet that is currently being loaded into the FIFO. Note that if the FIFO is double-buffered, FLUSH may have to be set twice to completely clear the FIFO. Important: This bit should only be set when the TXRDY bit is clear. At other times, it may cause data to be corrupted.
2	UNDRN	R/W	0	Underrun Value Description 0 No underrun. 1 An IN token has been received when TXRDY is not set.
1	FIFONE	R/W	0	Software must clear this bit. FIFO Not Empty Value Description 0 The FIFO is empty. 1 At least one packet is in the transmit FIFO.
0	TXRDY	R/W	0	Transmit Packet Ready Value Description 0 No transmit packet is ready. 1 Software sets this bit after loading a data packet into the TX FIFO. This bit is cleared automatically when a data packet has been transmitted. The FPD bit in the USRTYIS register is also set at this point.

transmitted. The \mathtt{EPn} bit in the $\mathtt{USBTXIS}$ register is also set at this point. \mathtt{TXRDY} is also automatically cleared prior to loading a second packet into a double-buffered FIFO.

Register 93: USB Transmit Control and Status Endpoint 1 High (USBTXCSRH1), offset 0x113

Register 94: USB Transmit Control and Status Endpoint 2 High (USBTXCSRH2), offset 0x123

Register 95: USB Transmit Control and Status Endpoint 3 High (USBTXCSRH3), offset 0x133

Register 96: USB Transmit Control and Status Endpoint 4 High (USBTXCSRH4), offset 0x143

Register 97: USB Transmit Control and Status Endpoint 5 High (USBTXCSRH5), offset 0x153

Register 98: USB Transmit Control and Status Endpoint 6 High (USBTXCSRH6), offset 0x163

Register 99: USB Transmit Control and Status Endpoint 7 High (USBTXCSRH7), offset 0x173




USBTXCSRHn is an 8-bit register that provides additional control for transfers through the currently selected transmit endpoint.



OTG A / Host Mode

USB Transmit Control and Status Endpoint n High (USBTXCSRHn)

Base 0x4005.0000 Offset 0x113 Type R/W, reset 0x00



Bit/Field	Name	Type	Reset	Description
7	AUTOSET	R/W	0	Auto Set

Value Description

- 0 The TXRDY bit must be set manually.
- 1 Enables the TXRDY bit to be automatically set when data of the maximum packet size (value in **USBTXMAXPn**) is loaded into the transmit FIFO. If a packet of less than the maximum packet size is loaded, then the TXRDY bit must be set manually.

Bit/Field	Name	Туре	Reset	Description
6	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
5	MODE	R/W	0	Mode
				Value Description
				0 Enables the endpoint direction as RX.
				1 Enables the endpoint direction as TX.
				Note: This bit only has an effect when the same endpoint FIFO is used for both transmit and receive transactions.
4	DMAEN	R/W	0	DMA Request Enable
				Value Description
				0 Disables the DMA request for the transmit endpoint.
				1 Enables the DMA request for the transmit endpoint.
				Note: 3 TX and 3 /RX endpoints can be connected to the μDMA module. If this bit is set for a particular endpoint, the DMAATX, DMABTX, or DMACTX field in the USB DMA Select (USBDMASEL) register must be programmed correspondingly.
3	FDT	R/W	0	Force Data Toggle
				Value Description
				0 No effect.
				1 Forces the endpoint DT bit to switch and the data packet to be cleared from the FIFO, regardless of whether an ACK was received. This bit can be used by interrupt transmit endpoints that are used to communicate rate feedback for isochronous endpoints.
2	DMAMOD	R/W	0	DMA Request Mode
				Value Description
				O An interrupt is generated after every DMA packet transfer.
				An interrupt is generated only after the entire DMA transfer is complete.
				Note: This bit must not be cleared either before or in the same cycle as the above DMAEN bit is cleared.
1	DTWE	R/W	0	Data Toggle Write Enable
				Value Description
				0 The DT bit cannot be written.
				1 Enables the current state of the transmit endpoint data to be written (see DT bit).
				This bit is automatically cleared once the new value is written.

1176 February 20, 2013

Bit/Field	Name	Type	Reset	Description
0	DT	R/W	0	Data Toggle


When read, this bit indicates the current state of the transmit endpoint data toggle.

If DTWE is High, this bit may be written with the required setting of the data toggle. If DTWE is Low, any value written to this bit is ignored. Care should be taken when writing to this bit as it should only be changed to RESET the transmit endpoint.

OTG B / Device Mode

USB Transmit Control and Status Endpoint n High (USBTXCSRHn)

Base 0x4005.0000 Offset 0x113 Type R/W, reset 0x00



Bit/Field	Name	Type	Reset	Description
7	AUTOSET	R/W	0	Auto Set
				Value Description
				0 The TXRDY bit must be set manually.
				1 Enables the TXRDY bit to be automatically set when data of the maximum packet size (value in USBTXMAXPn) is loaded into the transmit FIFO. If a packet of less than the maximum packet size is loaded, then the TXRDY bit must be set manually.
6	ISO	R/W	0	Isochronous Transfers
				Value Description
				0 Enables the transmit endpoint for bulk or interrupt transfers.
				1 Enables the transmit endpoint for isochronous transfers.
5	MODE	R/W	0	Mode
				Value Description

0 Enables the endpoint direction as RX.

Enables the endpoint direction as TX. 1

Note: This bit only has an effect where the same endpoint FIFO is used for both transmit and receive transactions.

Bit/Field	Name	Туре	Reset	Description
4	DMAEN	R/W	0	DMA Request Enable
				Value Description
				O Disables the DMA request for the transmit endpoint.
				1 Enables the DMA request for the transmit endpoint.
				Note: 3 TX and 3 RX endpoints can be connected to the μDMA module. If this bit is set for a particular endpoint, the DMAATX, DMABTX, or DMACTX field in the USB DMA Select (USBDMASEL) register must be programmed correspondingly.
3	FDT	R/W	0	Force Data Toggle
				Value Description
				0 No effect.
				Forces the endpoint DT bit to switch and the data packet to be cleared from the FIFO, regardless of whether an ACK was received. This bit can be used by interrupt transmit endpoints that are used to communicate rate feedback for isochronous endpoints.
2	DMAMOD	R/W	0	DMA Request Mode
				Value Description
				O An interrupt is generated after every DMA packet transfer.
				1 An interrupt is generated only after the entire DMA transfer is complete.
				Note: This bit must not be cleared either before or in the same cycle as the above DMAEN bit is cleared.
1:0	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.

Register 100: USB Maximum Receive Data Endpoint 1 (USBRXMAXP1), offset 0x114

Register 101: USB Maximum Receive Data Endpoint 2 (USBRXMAXP2), offset 0x124

Register 102: USB Maximum Receive Data Endpoint 3 (USBRXMAXP3), offset 0x134

Register 103: USB Maximum Receive Data Endpoint 4 (USBRXMAXP4), offset 0x144

Register 104: USB Maximum Receive Data Endpoint 5 (USBRXMAXP5), offset 0x154

Register 105: USB Maximum Receive Data Endpoint 6 (USBRXMAXP6), offset 0x164

Register 106: USB Maximum Receive Data Endpoint 7 (USBRXMAXP7), offset 0x174

OTG A /

The **USBRXMAXPn** is a 16-bit register which defines the maximum amount of data that can be transferred through the selected receive endpoint in a single operation.

OTG B /


Bits 10:0 define (in bytes) the maximum payload transmitted in a single transaction. The value set can be up to 1024 bytes but is subject to the constraints placed by the *USB Specification* on packet sizes for bulk, interrupt and isochronous transfers in full-speed operations.

The total amount of data represented by the value written to this register must not exceed the FIFO size for the receive endpoint, and must not exceed half the FIFO size if double-buffering is required.

Note: USBRXMAXPn must be set to an even number of bytes for proper interrupt generation in µDMA Basic mode.

USB Maximum Receive Data Endpoint n (USBRXMAXPn)

Base 0x4005.0000 Offset 0x114 Type R/W, reset 0x0000



Bit/Field	Name	Туре	Reset	Description
15:11	reserved	RO	0x0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
10:0	MAXLOAD	R/W	0x000	Maximum Payload

The maximum payload in bytes per transaction.

February 20, 2013 1179

Register 107: USB Receive Control and Status Endpoint 1 Low (USBRXCSRL1), offset 0x116

Register 108: USB Receive Control and Status Endpoint 2 Low (USBRXCSRL2), offset 0x126

Register 109: USB Receive Control and Status Endpoint 3 Low (USBRXCSRL3), offset 0x136

Register 110: USB Receive Control and Status Endpoint 4 Low (USBRXCSRL4), offset 0x146

Register 111: USB Receive Control and Status Endpoint 5 Low (USBRXCSRL5), offset 0x156

Register 112: USB Receive Control and Status Endpoint 6 Low (USBRXCSRL6), offset 0x166

Register 113: USB Receive Control and Status Endpoint 7 Low (USBRXCSRL7), offset 0x176




USBRXCSRLn is an 8-bit register that provides control and status bits for transfers through the currently selected receive endpoint.



OTG A / Host Mode

USB Receive Control and Status Endpoint n Low (USBRXCSRLn)

Base 0x4005.0000 Offset 0x116 Type R/W, reset 0x00



Bit/Field	Name	Type	Reset	Description
7	CLRDT	W1C	0	Clear Data Togg

Writing a 1 to this bit clears the \mathtt{DT} bit in the **USBRXCSRHn** register.

Bit/Field	Name	Туре	Reset	Description
6	STALLED	R/W	0	Endpoint Stalled
				 Value Description 0 A STALL handshake has not been received. 1 A STALL handshake has been received. The EPn bit in the
				USBRXIS register is also set.
				Software must clear this bit.
5	REQPKT	R/W	0	Request Packet
				Value Description 0 No request. 1 Requests an IN transaction.
				This bit is cleared when RXRDY is set.
4	FLUSH	R/W	0	Flush FIFO
3	DATAERR / NAKTO	R/W	0	Value Description No effect. Flushes the next packet to be read from the endpoint receive FIFO. The FIFO pointer is reset and the RXRDY bit is cleared. Note that if the FIFO is double-buffered, FLUSH may have to be set twice to completely clear the FIFO. Important: This bit should only be set when the RXRDY bit is set. At other times, it may cause data to be corrupted. Data Error / NAK Timeout Value Description Normal operation. Sochronous endpoints only: Indicates that RXRDY is set and the data packet has a CRC or bit-stuff error. This bit is cleared when RXRDY is cleared. Bulk endpoints only: Indicates that the receive endpoint is halted
2	ERROR	R/W	0	following the receipt of NAK responses for longer than the time set by the NAKLMT field in the USBRXINTERVALn register. Software must clear this bit to allow the endpoint to continue. Error Value Description 0 No error. 1 Three attempts have been made to receive a packet and no data packet has been received. The EPn bit in the USBRXIS register is set in this situation. Software must clear this bit.
				Note: This bit is only valid when the receive endpoint is operating in Bulk or Interrupt mode. In Isochronous mode, it always returns zero.

February 20, 2013 1181

Bit/Field	Name	Type	Reset	Description
1	FULL	RO	0	FIFO Full
				Value Description The receive FIFO is not full. No more packets can be loaded into the receive FIFO.
0	RXRDY	R/W	0	Receive Packet Ready

Value Description


- 0 No data packet has been received.
- A data packet has been received. The EPn bit in the USBRXIS register is also set in this situation.

If the AUTOCLR bit in the **USBRXCSRHn** register is set, then the this bit is automatically cleared when a packet of **USBRXMAXPn** bytes has been unloaded from the receive FIFO. If the AUTOCLR bit is clear, or if packets of less than the maximum packet size are unloaded, then software must clear this bit manually when the packet has been unloaded from the receive FIFO.

OTG B / Device Mode

USB Receive Control and Status Endpoint n Low (USBRXCSRLn)

Base 0x4005.0000 Offset 0x116 Type R/W, reset 0x00



Neset 0 0	Ů Ů	0 0	Ü	V
Bit/Field	Name	Туре	Reset	Description
7	CLRDT	W1C	0	Clear Data Toggle Writing a 1 to this bit clears the DT bit in the USBRXCSRHn register.

6 STALLED R/W 0 Endpoint Stalled

Value Description

- 0 A STALL handshake has not been transmitted.
- 1 A STALL handshake has been transmitted.

Software must clear this bit.

Bit/Field	Name	Туре	Reset	Description
5	STALL	R/W	0	Send STALL
				Value Description 0 No effect. 1 Issues a STALL handshake. Software must clear this bit to terminate the STALL condition. Note: This bit has no effect where the endpoint is being used for isochronous transfers.
4	FLUSH	R/W	0	Flush FIFO
4	1 20311	NW	Ü	Value Description No effect. Flushes the next packet from the endpoint receive FIFO. The FIFO pointer is reset and the RXRDY bit is cleared. The CPU writes a 1 to this bit to flush the next packet to be read from the endpoint receive FIFO. The FIFO pointer is reset and the RXRDY bit is cleared. Note that if the FIFO is double-buffered, FLUSH may have to be set twice to completely clear the FIFO.
				Important: This bit should only be set when the RXRDY bit is set. At other times, it may cause data to be corrupted.
3	DATAERR	RO	0	Data Error Value Description 0 Normal operation. 1 Indicates that RXRDY is set and the data packet has a CRC or bit-stuff error.
				This bit is cleared when RXRDY is cleared.
				Note: This bit is only valid when the endpoint is operating in Isochronous mode. In Bulk mode, it always returns zero.
2	OVER	R/W	0	Overrun Value Description No overrun error. Indicates that an OUT packet cannot be loaded into the receive FIFO.
				Software must clear this bit.
				Note: This bit is only valid when the endpoint is operating in Isochronous mode. In Bulk mode, it always returns zero.
1	FULL	RO	0	FIFO Full
				Value Description The receive FIFO is not full. No more packets can be loaded into the receive FIFO.

February 20, 2013 1183

Bit/Field	Name	Type	Reset	Description	
0	RXRDY	R/W	0	Receive Packet Ready	
				Value Description	

- 0 No data packet has been received.
- A data packet has been received. The EPn bit in the USBRXIS register is also set in this situation.

If the AUTOCLR bit in the **USBRXCSRHn** register is set, then the this bit is automatically cleared when a packet of **USBRXMAXPn** bytes has been unloaded from the receive FIFO. If the AUTOCLR bit is clear, or if packets of less than the maximum packet size are unloaded, then software must clear this bit manually when the packet has been unloaded from the receive FIFO.

Register 114: USB Receive Control and Status Endpoint 1 High (USBRXCSRH1), offset 0x117

Register 115: USB Receive Control and Status Endpoint 2 High (USBRXCSRH2), offset 0x127

Register 116: USB Receive Control and Status Endpoint 3 High (USBRXCSRH3), offset 0x137

Register 117: USB Receive Control and Status Endpoint 4 High (USBRXCSRH4), offset 0x147

Register 118: USB Receive Control and Status Endpoint 5 High (USBRXCSRH5), offset 0x157

Register 119: USB Receive Control and Status Endpoint 6 High (USBRXCSRH6), offset 0x167

Register 120: USB Receive Control and Status Endpoint 7 High (USBRXCSRH7), offset 0x177




USBRXCSRHn is an 8-bit register that provides additional control and status bits for transfers through the currently selected receive endpoint.



OTG A / Host Mode

USB Receive Control and Status Endpoint n High (USBRXCSRHn)

Base 0x4005.0000 Offset 0x117 Type R/W, reset 0x00




Bit/Field	Name	Туре	Reset	Description
7	AUTOCL	R/W	0	Auto Clear
				Value Description
				0 No effect.
				1 Enables the RXRDY bit to be automatically cleared when a packet of USBRXMAXPn bytes has been unloaded from the receive FIFO. When packets of less than the maximum packet size are unloaded, RXRDY must be cleared manually. Care must be taken when using μDMA to unload the receive FIFO as data is read from the receive FIFO in 4 byte chunks regardless of the value of the MAXLOAD field in the USBRXMAXPn register, see "DMA Operation" on page 1117.
6	AUTORQ	R/W	0	Auto Request
				Value Description
				0 No effect.
				1 Enables the REQPKT bit to be automatically set when the RXRDY bit is cleared.
				Note: This bit is automatically cleared when a short packet is received.
5	DMAEN	R/W	0	DMA Request Enable
				Value Description
				0 Disables the μDMA request for the receive endpoint.
				1 Enables the μDMA request for the receive endpoint.
				Note: 3 TX and 3 RX endpoints can be connected to the μDMA module. If this bit is set for a particular endpoint, the DMAARX, DMABRX, or DMACRX field in the USB DMA Select (USBDMASEL) register must be programmed correspondingly.
4	PIDERR	RO	0	PID Error
				Value Description
				0 No error.
				1 Indicates a PID error in the received packet of an isochronous transaction.
				This bit is ignored in bulk or interrupt transactions.
3	DMAMOD	R/W	0	DMA Request Mode
				Value Description
				0 An interrupt is generated after every μDMA packet transfer.
				1 An interrupt is generated only after the entire μDMA transfer is complete.
				Note: This bit must not be cleared either before or in the same cycle as the above DMAEN bit is cleared.

Bit/Field	Name	Туре	Reset	Description
2	DTWE	RO	0	Data Toggle Write Enable
				Value Description
				0 The DT bit cannot be written.
				Enables the current state of the receive endpoint data to be written (see DT bit).
				This bit is automatically cleared once the new value is written.
1	DT	RO	0	Data Toggle When read, this bit indicates the current state of the receive data toggle. If DTWE is High, this bit may be written with the required setting of the
				data toggle. If DTWE is Low, any value written to this bit is ignored. Care should be taken when writing to this bit as it should only be changed to RESET the receive endpoint.
0	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.

OTG B / Device Mode

USB Receive Control and Status Endpoint n High (USBRXCSRHn)

Base 0x4005.0000 Offset 0x117 Type R/W, reset 0x00



Bit/Field	Name	Туре	Reset	Description
7	AUTOCI	R/W	0	Auto Clear

Value Description

- 0 No effect.
- 1 Enables the RXRDY bit to be automatically cleared when a packet of **USBRXMAXPn** bytes has been unloaded from the receive FIFO. When packets of less than the maximum packet size are unloaded, RXRDY must be cleared manually. Care must be taken when using µDMA to unload the receive FIFO as data is read from the receive FIFO in 4 byte chunks regardless of the value of the MAXLOAD field in the **USBRXMAXPn** register, see "DMA Operation" on page 1117.

Bit/Field	Name	Туре	Reset	Description	
6	ISO	R/W	0	Isochronous Transfers	
				 Value Description Enables the receive endpoint for isochronous transfers. Enables the receive endpoint for bulk/interrupt transfers. 	
5	DMAEN	R/W	0	DMA Request Enable	
				Value Description	
				0 Disables the μDMA request for the receive endpoint.	
				1 Enables the μDMA request for the receive endpoint.	
				Note: 3 TX and 3 RX endpoints can be connected to the μDMA module. If this bit is set for a particular endpoint, the DMAARX, DMABRX, or DMACRX field in the USB DMA Select (USBDMASEL) register must be programmed correspondingly.	
4	DISNYET / PIDERR	R/W	0	Disable NYET / PID Error	
				Value Description	
				0 No effect.	
				1 For bulk or interrupt transactions: Disables the sending of NYET handshakes. When this bit is set, all successfully received packets are acknowledged, including at the point at which the FIFO becomes full.	
				For isochronous transactions: Indicates a PID error in the received packet.	
3	DMAMOD	R/W	0	DMA Request Mode	
				Value Description	
				0 An interrupt is generated after every μDMA packet transfer.	
				1 An interrupt is generated only after the entire μDMA transfer is complete.	
				Note: This bit must not be cleared either before or in the same cycle as the above DMAEN bit is cleared.	
2:0	reserved	RO	0x0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.	

Register 121: USB Receive Byte Count Endpoint 1 (USBRXCOUNT1), offset 0x118

Register 122: USB Receive Byte Count Endpoint 2 (USBRXCOUNT2), offset 0x128

Register 123: USB Receive Byte Count Endpoint 3 (USBRXCOUNT3), offset 0x138

Register 124: USB Receive Byte Count Endpoint 4 (USBRXCOUNT4), offset 0x148

Register 125: USB Receive Byte Count Endpoint 5 (USBRXCOUNT5), offset 0x158

Register 126: USB Receive Byte Count Endpoint 6 (USBRXCOUNT6), offset 0x168

Register 127: USB Receive Byte Count Endpoint 7 (USBRXCOUNT7), offset 0x178

OTG A /

Note: The value returned changes as the FIFO is unloaded and is only valid while the RXRDY bit in the **USBRXCSRLn** register is set.


USBRXCOUNTn is a 16-bit read-only register that holds the number of data bytes in the packet currently in line to be read from the receive FIFO. If the packet is transmitted as multiple bulk packets, the number given is for the combined packet.

OTG B /
Device

USB Receive Byte Count Endpoint n (USBRXCOUNTn)

Base 0x4005.0000 Offset 0x118

Type RO, reset 0x0000



Bit/Field	Name	Type	Reset	Description
15:13	reserved	RO	0x0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
12:0	COUNT	RO	0x000	Receive Packet Count Indicates the number of bytes in the receive packet.

Register 128: USB Host Transmit Configure Type Endpoint 1 (USBTXTYPE1), offset 0x11A

Register 129: USB Host Transmit Configure Type Endpoint 2 (USBTXTYPE2), offset 0x12A

Register 130: USB Host Transmit Configure Type Endpoint 3 (USBTXTYPE3), offset 0x13A

Register 131: USB Host Transmit Configure Type Endpoint 4 (USBTXTYPE4), offset 0x14A

Register 132: USB Host Transmit Configure Type Endpoint 5 (USBTXTYPE5), offset 0x15A

Register 133: USB Host Transmit Configure Type Endpoint 6 (USBTXTYPE6), offset 0x16A


Register 134: USB Host Transmit Configure Type Endpoint 7 (USBTXTYPE7), offset 0x17A



USBTXTYPEn is an 8-bit register that must be written with the endpoint number to be targeted by the endpoint, the transaction protocol to use for the currently selected transmit endpoint, and its operating speed.

USB Host Transmit Configure Type Endpoint n (USBTXTYPEn)

Base 0x4005.0000 Offset 0x11A Type R/W, reset 0x00



Bit/Field	Name	Туре	Reset	Description
7:6	SPEED	R/W	0x0	Operating Speed

This bit field specifies the operating speed of the target Device:

Value Description

0x0 Default

The target is assumed to be using the same connection speed as the USB controller.

0x1 Reserved

0x2 Full

0x3 Low

Bit/Field	Name	Туре	Reset	Description
5:4	PROTO	R/W	0x0	Protocol Software must configure this bit field to select the required protocol for the transmit endpoint:
				Value Description 0x0 Control 0x1 Isochronous 0x2 Bulk 0x3 Interrupt
3:0	TEP	R/W	0x0	Target Endpoint Number Software must configure this value to the endpoint number contained in the transmit endpoint descriptor returned to the USB controller during Device enumeration.

February 20, 2013 1191

Register 135: USB Host Transmit Interval Endpoint 1 (USBTXINTERVAL1), offset 0x11B

Register 136: USB Host Transmit Interval Endpoint 2 (USBTXINTERVAL2), offset 0x12B

Register 137: USB Host Transmit Interval Endpoint 3 (USBTXINTERVAL3), offset 0x13B

Register 138: USB Host Transmit Interval Endpoint 4 (USBTXINTERVAL4), offset 0x14B

Register 139: USB Host Transmit Interval Endpoint 5 (USBTXINTERVAL5), offset 0x15B

Register 140: USB Host Transmit Interval Endpoint 6 (USBTXINTERVAL6), offset 0x16B

Register 141: USB Host Transmit Interval Endpoint 7 (USBTXINTERVAL7), offset 0x17B




USBTXINTERVALn is an 8-bit register that, for interrupt and isochronous transfers, defines the polling interval for the currently selected transmit endpoint. For bulk endpoints, this register defines the number of frames after which the endpoint should time out on receiving a stream of NAK responses.

The **USBTXINTERVALn** register value defines a number of frames, as follows:

Transfer Type	Speed	Valid values (m)	Interpretation
Interrupt	Low-Speed or Full-Speed	0x01 – 0xFF	The polling interval is <i>m</i> frames.
Isochronous	Full-Speed	0x01 – 0x10	The polling interval is $2^{(m-1)}$ frames/micorframes
Bulk	Full-Speed	0x02 – 0x10	The NAK Limit is 2 ^(m-1) frames/microframes. A value of 0 or 1 disables the NAK timeout function.

USB Host Transmit Interval Endpoint n (USBTXINTERVALn)

Base 0x4005.0000 Offset 0x11B Type R/W, reset 0x00



Bit/Field	Name	Туре	Reset	Description
7:0	TXPOLL / NAKLMT	R/W	0x00	TX Polling / NAK Limit

The polling interval for interrupt/isochronous transfers; the NAK limit for bulk transfers. See table above for valid entries; other values are reserved.

Register 142: USB Host Configure Receive Type Endpoint 1 (USBRXTYPE1), offset 0x11C

Register 143: USB Host Configure Receive Type Endpoint 2 (USBRXTYPE2), offset 0x12C

Register 144: USB Host Configure Receive Type Endpoint 3 (USBRXTYPE3), offset 0x13C

Register 145: USB Host Configure Receive Type Endpoint 4 (USBRXTYPE4), offset 0x14C

Register 146: USB Host Configure Receive Type Endpoint 5 (USBRXTYPE5), offset 0x15C

Register 147: USB Host Configure Receive Type Endpoint 6 (USBRXTYPE6), offset 0x16C


Register 148: USB Host Configure Receive Type Endpoint 7 (USBRXTYPE7), offset 0x17C



USBRXTYPEn is an 8-bit register that must be written with the endpoint number to be targeted by the endpoint, the transaction protocol to use for the currently selected receive endpoint, and its operating speed.

USB Host Configure Receive Type Endpoint n (USBRXTYPEn)

Base 0x4005.0000 Offset 0x11C Type R/W, reset 0x00



Bit/Field	Name	Туре	Reset	Description
7:6	SPEED	R/W	0x0	Operating Speed

This bit field specifies the operating speed of the target Device:

Value Description

0x0 Default

The target is assumed to be using the same connection speed as the USB controller.

0x1 Reserved

0x2 Full

0x3 Low

Bit/Field	Name	Туре	Reset	Description
5:4	PROTO	R/W	0x0	Protocol Software must configure this bit field to select the required protocol for the receive endpoint:
				Value Description 0x0 Control 0x1 Isochronous 0x2 Bulk 0x3 Interrupt
3:0	TEP	R/W	0x0	Target Endpoint Number Software must set this value to the endpoint number contained in the receive endpoint descriptor returned to the USB controller during Device enumeration.

Register 149: USB Host Receive Polling Interval Endpoint 1 (USBRXINTERVAL1), offset 0x11D

Register 150: USB Host Receive Polling Interval Endpoint 2 (USBRXINTERVAL2), offset 0x12D

Register 151: USB Host Receive Polling Interval Endpoint 3 (USBRXINTERVAL3), offset 0x13D

Register 152: USB Host Receive Polling Interval Endpoint 4 (USBRXINTERVAL4), offset 0x14D

Register 153: USB Host Receive Polling Interval Endpoint 5 (USBRXINTERVAL5), offset 0x15D

Register 154: USB Host Receive Polling Interval Endpoint 6 (USBRXINTERVAL6), offset 0x16D

Register 155: USB Host Receive Polling Interval Endpoint 7 (USBRXINTERVAL7), offset 0x17D


OTG A / Host **USBRXINTERVALn** is an 8-bit register that, for interrupt and isochronous transfers, defines the polling interval for the currently selected receive endpoint. For bulk endpoints, this register defines the number of frames after which the endpoint should time out on receiving a stream of NAK responses.

The **USBRXINTERVALn** register value defines a number of frames, as follows:

Transfer Type	Speed	Valid values (m)	Interpretation
Interrupt	Low-Speed or Full-Speed	0x01 – 0xFF	The polling interval is <i>m</i> frames.
Isochronous	Full-Speed	0x01 – 0x10	The polling interval is $2^{(m-1)}$ frames/microframes.
Bulk	Full-Speed	0x02 – 0x10	The NAK Limit is 2 ^(m-1) frames/microframes. A value of 0 or 1 disables the NAK timeout function.

USB Host Receive Polling Interval Endpoint n (USBRXINTERVALn)

Base 0x4005.0000 Offset 0x11D Type R/W, reset 0x00



Bit/Field	Name	Туре	Reset	Description
7:0	TXPOLL / NAKLMT	R/W	0x00	RX Polling / NAK Limit

The polling interval for interrupt/isochronous transfers; the NAK limit for bulk transfers. See table above for valid entries; other values are reserved.

Register 156: USB Request Packet Count in Block Transfer Endpoint 1 (USBRQPKTCOUNT1), offset 0x304

Register 157: USB Request Packet Count in Block Transfer Endpoint 2 (USBRQPKTCOUNT2), offset 0x308

Register 158: USB Request Packet Count in Block Transfer Endpoint 3 (USBRQPKTCOUNT3), offset 0x30C

Register 159: USB Request Packet Count in Block Transfer Endpoint 4 (USBRQPKTCOUNT4), offset 0x310

Register 160: USB Request Packet Count in Block Transfer Endpoint 5 (USBRQPKTCOUNT5), offset 0x314

Register 161: USB Request Packet Count in Block Transfer Endpoint 6 (USBRQPKTCOUNT6), offset 0x318

Register 162: USB Request Packet Count in Block Transfer Endpoint 7 (USBRQPKTCOUNT7), offset 0x31C




This 16-bit read/write register is used in Host mode to specify the number of packets that are to be transferred in a block transfer of one or more bulk packets to receive endpoint n. The USB controller uses the value recorded in this register to determine the number of requests to issue where the AUTORO bit in the **USBRXCSRHn** register has been set. See "IN Transactions as a Host" on page 1113.

Note: Multiple packets combined into a single bulk packet within the FIFO count as one packet.

USB Request Packet Count in Block Transfer Endpoint n (USBRQPKTCOUNTn)

Base 0x4005.0000 Offset 0x304 Type R/W, reset 0x0000



Sets the number of packets of the size defined by the ${\tt MAXLOAD}$ bit field that are to be transferred in a block transfer.

Note: This is only used in Host mode when AUTORQ is set. The bit has no effect in Device mode or when AUTORQ is not set.

Register 163: USB Receive Double Packet Buffer Disable (USBRXDPKTBUFDIS), offset 0x340

OTG A / Host **USBRXDPKTBUFDIS** is a 16-bit register that indicates which of the receive endpoints have disabled the double-packet buffer functionality (see the section called "Double-Packet Buffering" on page 1109).

USB Receive Double Packet Buffer Disable (USBRXDPKTBUFDIS)

OTG B / Device Base 0x4005.0000 Offset 0x340 Type R/W, reset 0x0000

	15	14	13	12	11	10	9	8	7	6	5	4	3	2	1	0
	,			rese	rved I		1	1	EP7	EP6	EP5	EP4	EP3	EP2	EP1	reserved
Type	RO	RO	RO	RO	RO	RO	RO	RO	R/W	RO						
Reset	0	Ω	Ω	0	Ω	0	Ω	Ω	Ω	0	Ω	Ω	0	Ω	Ω	Ω

Bit/Field	Name	Type	Reset	Description
15:8	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
7	EP7	R/W	0	EP7 RX Double-Packet Buffer Disable
				Value Description
				0 Disables double-packet buffering.
				1 Enables double-packet buffering.
6	EP6	R/W	0	EP6 RX Double-Packet Buffer Disable Same description as EP7.
5	EP5	R/W	0	EP5 RX Double-Packet Buffer Disable Same description as EP7.
4	EP4	R/W	0	EP4 RX Double-Packet Buffer Disable Same description as EP7.
3	EP3	R/W	0	EP3 RX Double-Packet Buffer Disable Same description as EP7.
2	EP2	R/W	0	EP2 RX Double-Packet Buffer Disable Same description as EP7.
1	EP1	R/W	0	EP1 RX Double-Packet Buffer Disable Same description as EP7.
0	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.

Register 164: USB Transmit Double Packet Buffer Disable (USBTXDPKTBUFDIS), offset 0x342

OTG A / Host **USBTXDPKTBUFDIS** is a 16-bit register that indicates which of the transmit endpoints have disabled the double-packet buffer functionality (see the section called "Double-Packet Buffering" on page 1108).

USB Transmit Double Packet Buffer Disable (USBTXDPKTBUFDIS)

OTG B / Device Base 0x4005.0000 Offset 0x342 Type R/W, reset 0x0000

	15	14	13	12	11	10	9	8	7	6	5	4	3	2	1	0
				rese	rved			1	EP7	EP6	EP5	EP4	EP3	EP2	EP1	reserved
Type [®]	RO	RO	RO	RO	RO	RO	RO	RO	R/W	RO						
Reset	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0

Bit/Field	Name	Type	Reset	Description
15:8	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
7	EP7	R/W	0	EP7 TX Double-Packet Buffer Disable
				Value Description
				0 Disables double-packet buffering.
				1 Enables double-packet buffering.
6	EP6	R/W	0	EP6 TX Double-Packet Buffer Disable Same description as EP7.
5	EP5	R/W	0	EP5 TX Double-Packet Buffer Disable Same description as EP7.
4	EP4	R/W	0	EP4 TX Double-Packet Buffer Disable Same description as EP7.
3	EP3	R/W	0	EP3 TX Double-Packet Buffer Disable
				Same description as EP7.
2	EP2	R/W	0	EP2 TX Double-Packet Buffer Disable
				Same description as EP7.
1	EP1	R/W	0	EP1 TX Double-Packet Buffer Disable
				Same description as EP7.
0	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.

Register 165: USB External Power Control (USBEPC), offset 0x400

OTG A / Host This 32-bit register specifies the function of the two-pin external power interface (USB0EPEN and USB0PFLT). The assertion of the power fault input may generate an automatic action, as controlled by the hardware configuration registers. The automatic action is necessary because the fault condition may require a response faster than one provided by firmware.

OTG B /
Device

7

USB External Power Control (USBEPC)

Base 0x4005.0000

Offset 0x400 Type R/W, reset 0x0000.0000

	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16
		1						rese	rved •					'		
Type	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO
Reset	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0
	15	14	13	12	11	10	9	8	7	6	5	4	3	2	1	0
		•	rese	rved		PFLTACT			reserved	PFLTAEN	PFLTSEN	PFLTEN	reserved	EPENDE	EP	EN
Туре	RO	RO	RO	RO	RO	RO	R/W	R/W	RO	R/W	R/W	R/W	RO	R/W	R/W	R/W
Reset	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0

Bit/Field	Name	Type	Reset	Description
31:10	reserved	RO	0x0000.0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
9:8	PFLTACT	R/W	0x0	Power Fault Action

This bit field specifies how the USBOEPEN signal is changed when detecting a USB power fault.

Value Description 0x0 Unchanged

 $\tt USB0EPEN$ is controlled by the combination of the $\tt EPEN$ and $\tt EPENDE$ bits.

0x1 Tristate

USB0EPEN is undriven (tristate).

0x2 Low

USB0EPEN is driven Low.

0x3 High

USB0EPEN is driven High.

reserved RO 0 Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.

Bit/Field	Name	Туре	Reset	Description
6	PFLTAEN	R/W	0	Power Fault Action Enable
				This bit specifies whether a USB power fault triggers any automatic corrective action regarding the driven state of the USB0EPEN signal.
				Value Description
				0 Disabled
				$\tt USB0EPEN$ is controlled by the combination of the $\tt EPEN$ and $\tt EPENDE$ bits.
				1 Enabled
				The ${\tt USB0EPEN}$ output is automatically changed to the state specified by the ${\tt PFLTACT}$ field.
5	PFLTSEN	R/W	0	Power Fault Sense
				This bit specifies the logical sense of the ${\tt USBOPFLT}$ input signal that indicates an error condition.
				The complementary state is the inactive state.
				Value Description
				0 Low Fault
				If USB0PFLT is driven Low, the power fault is signaled internally (if enabled by the PFLTEN bit).
				1 High Fault
				If ${\tt USBOPFLT}$ is driven High, the power fault is signaled internally (if enabled by the ${\tt PFLTEN}$ bit).
4	PFLTEN	R/W	0	Power Fault Input Enable
				This bit specifies whether the ${\tt USB0PFLT}$ input signal is used in internal logic.
				Value Description
				0 Not Used
				The USBOPFLT signal is ignored.
				1 Used
				The USBOPFLT signal is used internally.
3	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.

Bit/Field	Name	Туре	Reset	Description
2	EPENDE	R/W	0	EPEN Drive Enable This bit specifies whether the USB0EPEN signal is driven or undriven (tristate). When driven, the signal value is specified by the EPEN field. When not driven, the EPEN field is ignored and the USB0EPEN signal is placed in a high-impedance state. Value Description Not Driven The USB0EPEN signal is high impedance. Driven The USB0EPEN signal is driven to the logical value specified by the value of the EPEN field. The USB0EPEN signal is undriven at reset because the sense of the external power supply enable is unknown. By adding the high-impedance state, system designers may bias the power supply enable to the disabled state using a large resistor (100 kΩ) and later configure and
1:0	EPEN	R/W	0x0	drive the output signal to enable the power supply. External Power Supply Enable Configuration This bit field specifies and controls the logical value driven on the USB0EPEN signal. Value Description Ox0 Power Enable Active Low The USB0EPEN signal is driven Low if the EPENDE bit is set. Ox1 Power Enable Active High The USB0EPEN signal is driven High if the EPENDE bit is set. Ox2 Power Enable High if VBUS Low The USB0EPEN signal is driven High when the A device is not recognized. Ox3 Power Enable High if VBUS High The USB0EPEN signal is driven High when the A device is recognized.

Register 166: USB External Power Control Raw Interrupt Status (USBEPCRIS), offset 0x404

OTG A / Host


This 32-bit register specifies the unmasked interrupt status of the two-pin external power interface.

USB External Power Control Raw Interrupt Status (USBEPCRIS)

Base 0x4005.0000

Offset 0x404 Type RO, reset 0x0000.0000

OTG B / **Device**



Bit/Field	Name	Type	Reset	Description
31:1	reserved	RO	0x0000.000	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
0	PF	RO	0	USB Power Fault Interrupt Status

Value Description

- 1 A Power Fault status has been detected.
- 0 An interrupt has not occurred.

This bit is cleared by writing a 1 to the PF bit in the **USBEPCISC** register.

Register 167: USB External Power Control Interrupt Mask (USBEPCIM), offset 0x408

OTG A / Host


This 32-bit register specifies the interrupt mask of the two-pin external power interface.

USB External Power Control Interrupt Mask (USBEPCIM)

Base 0x4005.0000

Offset 0x408 Type R/W, reset 0x0000.0000

OTG B / **Device**



Bit/Field	Name	Type	Reset	Description
31:1	reserved	RO	0x0000.000	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
0	PF	R/W	0	USB Power Fault Interrupt Mask

Value Description


- The raw interrupt signal from a detected power fault is sent to the interrupt controller.
- A detected power fault does not affect the interrupt status. 0

Register 168: USB External Power Control Interrupt Status and Clear (USBEPCISC), offset 0x40C

OTG A / Host This 32-bit register specifies the masked interrupt status of the two-pin external power interface. It also provides a method to clear the interrupt state.

USB External Power Control Interrupt Status and Clear (USBEPCISC)

OTG B / Device Base 0x4005.0000 Offset 0x40C Type R/W, reset 0x0000.0000



Bit/Field	Name	Type	Reset	Description
31:1	reserved	RO	0x0000.000	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
0	PF	R/W1C	0	USB Power Fault Interrupt Status and Clear

Value Description

- 1 The PF bits in the USBEPCRIS and USBEPCIM registers are set, providing an interrupt to the interrupt controller.
- 0 No interrupt has occurred or the interrupt is masked.


This bit is cleared by writing a 1. Clearing this bit also clears the ${\tt PF}$ bit in the **USBEPCRIS** register.

Register 169: USB Device RESUME Raw Interrupt Status (USBDRRIS), offset 0x410

OTG A / Host The **USBDRRIS** 32-bit register is the raw interrupt status register. On a read, this register gives the current raw status value of the corresponding interrupt prior to masking. A write has no effect.

USB Device RESUME Raw Interrupt Status (USBDRRIS)

OTG B / Device Base 0x4005.0000 Offset 0x410 Type RO, reset 0x0000.0000



Bit/Field	Name	Type	Reset	Description
31:1	reserved	RO	0x0000.000	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
0	RESUME	RO	0	RESUME Interrupt Status

Value Description

0 An interrupt has not occurred.

1 A RESUME status has been detected.

This bit is cleared by writing a 1 to the ${\tt RESUME}$ bit in the ${\tt USBDRISC}$ register.

Register 170: USB Device RESUME Interrupt Mask (USBDRIM), offset 0x414




The **USBDRIM** 32-bit register is the masked interrupt status register. On a read, this register gives the current value of the mask on the corresponding interrupt. Setting a bit sets the mask, preventing the interrupt from being signaled to the interrupt controller. Clearing a bit clears the corresponding mask, enabling the interrupt to be sent to the interrupt controller.

OTG B / Device

USB Device RESUME Interrupt Mask (USBDRIM)

Base 0x4005.0000

Offset 0x414 Type R/W, reset 0x0000.0000



Bit/Field	Name	Type	Reset	Description
31:1	reserved	RO	0x00	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
0	RESUME	R/W	0	RESUME Interrupt Mask

Value Description

- 1 The raw interrupt signal from a detected RESUME is sent to the interrupt controller. This bit should only be set when a SUSPEND has been detected (the SUSPEND bit in the **USBIS** register is set).
- 0 A detected RESUME does not affect the interrupt status.


Register 171: USB Device RESUME Interrupt Status and Clear (USBDRISC), offset 0x418

OTG A /

The **USBDRISC** 32-bit register is the interrupt clear register. On a write of 1, the corresponding interrupt is cleared. A write of 0 has no effect.

USB Device RESUME Interrupt Status and Clear (USBDRISC)

OTG B / Device Base 0x4005.0000 Offset 0x418 Type W1C, reset 0x0000.0000



Bit/Field	Name	Type	Reset	Description
31:1	reserved	RO	0x0000.000	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
0	RESUME	R/W1C	0	RESUME Interrupt Status and Clear

Value Description

- 1 The RESUME bits in the **USBDRRIS** and **USBDRCIM** registers are set, providing an interrupt to the interrupt controller.
- 0 No interrupt has occurred or the interrupt is masked.

This bit is cleared by writing a 1. Clearing this bit also clears the $\tt RESUME$ bit in the **USBDRCRIS** register.

Register 172: USB General-Purpose Control and Status (USBGPCS), offset 0x41C

OTG A /

OTG B /
Device

USBGPCS provides the state of the internal ID signal.


When used in OTG mode, USB0VBUS and USB0ID do not require any configuration as they are dedicated pins for the USB controller and directly connect to the USB connector's VBUS and ID signals. If the USB controller is used as either a dedicated Host or Device, the DEVMODOTG and DEVMOD bits in the **USB General-Purpose Control and Status** (USBGPCS) register can be used to connect the USB0VBUS and USB0ID inputs to fixed levels internally, freeing the PB0 and PB1 pins for GPIO use. For proper self-powered Device operation, the VBUS value must still be monitored to assure that if the Host removes VBUS, the self-powered Device disables the D+/D- pull-up resistors. This function can be

The termination resistors for the USB PHY have been added internally, and thus there is no need for external resistors. For a device, there is a 1.5 KOhm pull-up on the D+ and for a host there are 15 KOhm pull-downs on both D+ and D-.

USB General-Purpose Control and Status (USBGPCS)

Base 0x4005.0000 Offset 0x41C

Type R/W, reset 0x0000.0003



accomplished by connecting a standard GPIO to VBUS.

			-	
Bit/Field	Name	Туре	Reset	Description
31:2	reserved	RO	0x0000.000	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
1	DEVMODOTG	R/W	1	Enable Device Mode
				This bit enables the ${\tt DEVMOD}$ bit to control the state of the internal ID signal in OTG mode.
				Value Description
				The mode is specified by the state of the internal ID signal.
				1 This bit enables the DEVMOD bit to control the internal ID signal.
0	DEVMOD	R/W	1	Device Mode
				This bit specifies the state of the internal ID signal in Host mode and in OTG mode when the DEVMODOTG bit is set.
				In Device mode this bit is ignored (assumed set).
				Value Description
				0 Host mode
				1 Device mode

Register 173: USB VBUS Droop Control (USBVDC), offset 0x430




This 32-bit register enables a controlled masking of VBUS to compensate for any in-rush current by a Device that is connected to the Host controller. The in-rush current can cause VBUS to droop, causing the USB controller's behavior to be unexpected. The USB Host controller allows VBUS to fall lower than the VBUS Valid level (4.75 V) but not below AValid (2.0 V) for 65 microseconds without signaling a VBUSERR interrupt in the controller. Without this, any glitch on VBUS would force the USB Host controller to remove power from VBUS and then re-enumerate the Device.

USB VBUS Droop Control (USBVDC)

Base 0x4005.0000 Offset 0x430

Dit/Fiold

Type R/W, reset 0x0000.0000



Bit/Field	ivame	туре	Reset	Description
31:1	reserved	RO	0x0000.000	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
0	VRDEN	RΛΜ	0	VRUS Droop Enable

Value Description

- 0 No effect.
- Any changes from VBUSVALID are masked when VBUS goes below 4.75 V but not lower than 2.0 V for 65 microseconds. During this time, the VBUS state indicates VBUSVALID.


Register 174: USB VBUS Droop Control Raw Interrupt Status (USBVDCRIS), offset 0x434



This 32-bit register specifies the unmasked interrupt status of the VBUS droop limit of 65 microseconds.

USB VBUS Droop Control Raw Interrupt Status (USBVDCRIS)

Offset 0x434 Type RO, reset 0x0000.0000



Bit/Field	Name	Type	Reset	Description
31:1	reserved	RO	0x0000.000	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
0	VD	RO	0	VBUS Droop Raw Interrupt Status

Value Description

- A VBUS droop lasting for 65 microseconds has been detected.
- 0 An interrupt has not occurred.

This bit is cleared by writing a 1 to the VD bit in the USBVDCISC register.

Register 175: USB VBUS Droop Control Interrupt Mask (USBVDCIM), offset 0x438


OTG A /

This 32-bit register specifies the interrupt mask of the VBUS droop.

USB VBUS Droop Control Interrupt Mask (USBVDCIM)

Base 0x4005.0000

Offset 0x438
Type R/W, reset 0x0000.0000



Bit/Field	Name	Type	Reset	Description
31:1	reserved	RO	0x0000.000	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
0	VD	R/W	0	VBUS Droop Interrupt Mask

Value Description

- 1 The raw interrupt signal from a detected VBUS droop is sent to the interrupt controller.
- 0 A detected VBUS droop does not affect the interrupt status.

Register 176: USB VBUS Droop Control Interrupt Status and Clear (USBVDCISC), offset 0x43C




This 32-bit register specifies the masked interrupt status of the VBUS droop and provides a method to clear the interrupt state.

USB VBUS Droop Control Interrupt Status and Clear (USBVDCISC)

Base 0x4005.0000

Offset 0x43C Type R/W, reset 0x0000.0000



Bit/Field	Name	Type	Reset	Description
31:1	reserved	RO	0x0000.000	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
0	VD	R/W1C	0	VBUS Droop Interrupt Status and Clear

Value Description

- 1 The VD bits in the USBVDCRIS and USBVDCIM registers are set, providing an interrupt to the interrupt controller.
- 0 No interrupt has occurred or the interrupt is masked.

This bit is cleared by writing a 1. Clearing this bit also clears the $\mathtt{V}\mathtt{D}$ bit in the USBVDCRIS register.

Register 177: USB ID Valid Detect Raw Interrupt Status (USBIDVRIS), offset 0x444


OTG

This 32-bit register specifies whether the unmasked interrupt status of the ID value is valid.

USB ID Valid Detect Raw Interrupt Status (USBIDVRIS)

Base 0x4005.0000

Offset 0x444
Type RO, reset 0x0000.0000



Bit/Field	Name	Type	Reset	Description
31:1	reserved	RO	0x0000.000	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
0	ID	RO	0	ID Valid Detect Raw Interrupt Status

Value Description

- 1 A valid ID has been detected.
- 0 An interrupt has not occurred.

This bit is cleared by writing a 1 to the ${\tt ID}$ bit in the ${\tt USBIDVISC}$ register.

Register 178: USB ID Valid Detect Interrupt Mask (USBIDVIM), offset 0x448


OTG

This 32-bit register specifies the interrupt mask of the ID valid detection.

USB ID Valid Detect Interrupt Mask (USBIDVIM)

Base 0x4005.0000 Offset 0x448

Type R/W, reset 0x0000.0000



Bit/Field	Name	Type	Reset	Description
31:1	reserved	RO	0x0000.000	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
0	ID	R/W	0	ID Valid Detect Interrupt Mask

Value Description

- 1 The raw interrupt signal from a detected ID valid is sent to the interrupt controller.
- 0 A detected ID valid does not affect the interrupt status.

Register 179: USB ID Valid Detect Interrupt Status and Clear (USBIDVISC), offset 0x44C


OTG

This 32-bit register specifies the masked interrupt status of the ID valid detect. It also provides a method to clear the interrupt state.

USB ID Valid Detect Interrupt Status and Clear (USBIDVISC)

Base 0x4005.0000

Offset 0x44C Type R/W1C, reset 0x0000.0000



Bit/Field	Name	Type	Reset	Description
31:1	reserved	RO	0x0000.000	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
0	ID	R/W1C	0	ID Valid Detect Interrupt Status and Clear

Value Description

- No interrupt has occurred or the interrupt is masked.
- 1 The ${\tt ID}$ bits in the **USBIDVRIS** and **USBIDVIM** registers are set, providing an interrupt to the interrupt controller.

This bit is cleared by writing a 1. Clearing this bit also clears the ${\tt ID}$ bit in the USBIDVRIS register.

Register 180: USB DMA Select (USBDMASEL), offset 0x450


OTG A /

This 32-bit register specifies which endpoints are mapped to the 6 allocated μDMA channels, see Table 9-1 on page 584 for more information on channel assignments.

USB DMA Select (USBDMASEL)

OTG B /
Device

Base 0x4005.0000 Offset 0x450 Type R/W, reset 0x0033.2211



Bit/Field	Name	Type	Reset	Description
31:24	reserved	RO	0x00	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
23:20	DMACTX	R/W	0x3	DMA C TX Select

Specifies the TX mapping of the third USB endpoint on μDMA channel 5 (primary assignment).

Value	Description
0x0	reserved
0x1	Endpoint 1 TX
0x2	Endpoint 2 TX
0x3	Endpoint 3 TX
0x4	Endpoint 4 TX
0x5	Endpoint 5 TX
0x6	Endpoint 6 TX
0x7	Endpoint 7 TX
0x8 - 0xF	reserved

Bit/Field	Name	Туре	Reset	Description
19:16	DMACRX	R/W	0x3	DMA C RX Select Specifies the RX and TX mapping of the third USB endpoint on μ DMA channel 4 (primary assignment).
				Value Description
				0x0 reserved
				0x1 Endpoint 1 RX
				0x2 Endpoint 2 RX
				0x3 Endpoint 3 RX
				0x4 Endpoint 4 RX
				0x5 Endpoint 5 RX
				0x6 Endpoint 6 RX
				0x7 Endpoint 7 RX
				0x8 - 0xF reserved
15:12	DMABTX	R/W	0x2	DMA B TX Select Specifies the TX mapping of the second USB endpoint on µDMA channel 3 (primary assignment). Same bit definitions as the DMACTX field.
11:8	DMABRX	R/W	0x2	DMA B RX Select
11.0	DIVIABRA	NW	UXZ	Specifies the RX mapping of the second USB endpoint on µDMA channel 2 (primary assignment). Same bit definitions as the DMACRX field.
7:4	DMAATX	R/W	0x1	DMA A TX Select Specifies the TX mapping of the first USB endpoint on µDMA channel 1 (primary assignment). Same bit definitions as the DMACTX field.
3:0	DMAARX	R/W	0x1	DMA A RX Select Specifies the RX mapping of the first USB endpoint on µDMA channel 0 (primary assignment). Same bit definitions as the DMACRX field.


Register 181: USB Peripheral Properties (USBPP), offset 0xFC0

The **USBPP** register provides information regarding the properties of the USB module.

USB Peripheral Properties (USBPP)

Base 0x4005.0000 Offset 0xFC0

Type RO, reset 0x0000.10D0



compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.

RO 0x1 PHY Present

Value Description

0 A PHY is not integrated with the USB MAC.

1 A PHY is integrated with the USB MAC.

3:0 TYPE RO 0x0 Controller Type

PHY

4

Value Description

0x0 The first-generation USB controller.

0x1 - 0xF Reserved

19 Analog Comparators

An analog comparator is a peripheral that compares two analog voltages and provides a logical output that signals the comparison result.

Note: Not all comparators have the option to drive an output pin. See "Signal Description" on page 1220 for more information.

The comparator can provide its output to a device pin, acting as a replacement for an analog comparator on the board. In addition, the comparator can signal the application via interrupts or trigger the start of a sample sequence in the ADC. The interrupt generation and ADC triggering logic is separate and independent. This flexibility means, for example, that an interrupt can be generated on a rising edge and the ADC triggered on a falling edge.

The Stellaris[®] LM4F232H5QC microcontroller provides three independent integrated analog comparators with the following functions:

- Compare external pin input to external pin input or to internal programmable voltage reference
- Compare a test voltage against any one of the following voltages:
 - An individual external reference voltage
 - A shared single external reference voltage
 - A shared internal reference voltage

19.1 Block Diagram

ve input Comparator 2 C2+ +ve input output C20 +ve input (alternate) ACCTL2 ACSTAT2 interrupt reference input C1ve input Comparator : +ve input output +ve input (alternate) ACCTL1 trigger ACSTAT1 interrupt reference input C0--ve input Comparator 0 C0+ -+ve input C0o +ve input (alternate) ACCTL0 trigger trigger ACSTAT0 interrupt reference input Voltage Interrupt Control Ref ACRIS Interrupt Internal ACREFCTL **ACMIS** Bus **ACINTEN** Module Status ACMPPP

Figure 19-1. Analog Comparator Module Block Diagram

Note:

This block diagram depicts the maximum number of analog comparators and comparator outputs for the family of microcontrollers; the number for this specific device may vary. See page 1233 for what is included on this device.

19.2 Signal Description

The following table lists the external signals of the Analog Comparators and describes the function of each. The Analog Comparator output signals are alternate functions for some GPIO signals and default to be GPIO signals at reset. The column in the table below titled "Pin Mux/Pin Assignment" lists the possible GPIO pin placements for the Analog Comparator signals. The AFSEL bit in the **GPIO Alternate Function Select (GPIOAFSEL)** register (page 670) should be set to choose the Analog Comparator function. The number in parentheses is the encoding that must be programmed into the PMCn field in the **GPIO Port Control (GPIOPCTL)** register (page 688) to assign the Analog Comparator signal to the specified GPIO port pin. The positive and negative input signals are configured by clearing the DEN bit in the **GPIO Digital Enable (GPIODEN)** register. For more information on configuring GPIOs, see "General-Purpose Input/Outputs (GPIOs)" on page 646.

Table 19-1. Analog Comparators Signals (100LQFP)

Pin Name	Pin Number	Pin Mux / Pin Assignment	Pin Type	Buffer Type ^a	Description
C0+	23	PC6	1	Analog	Analog comparator 0 positive input.

Pin Name Pin Number Pin Mux / Pin Pin Type Buffer Type^a Description **Assignment** 22 PC7 ı Analog Analog comparator 0 negative input. C0-COo 40 PF0 (9) 0 TTL Analog comparator 0 output. PC5 24 ı Analog Analog comparator 1 positive input. C1 +C1-25 PC4 Τ Analog Analog comparator 1 negative input. 0 41 PF1 (9) TTL Analog comparator 1 output. C1o 87 PG6 I Analog Analog comparator 2 positive input. C2+ PG7 ı C2-Analog Analog comparator 2 negative input. PF2 (9) C2o 42 0 TTL Analog comparator 2 output.

Table 19-1. Analog Comparators Signals (100LQFP) (continued)


19.3 Functional Description

The comparator compares the VIN- and VIN+ inputs to produce an output, VOUT.

```
VIN- < VIN+, VOUT = 1
VIN- > VIN+, VOUT = 0
```

As shown in Figure 19-2 on page 1221, the input source for VIN- is an external input, Cn-, where n is the analog comparator number. In addition to an external input, Cn+, input sources for VIN+ can be the C0+ or an internal reference, V_{IREF} .

Figure 19-2. Structure of Comparator Unit



A comparator is configured through two status/control registers, Analog Comparator Control (ACCTL) and Analog Comparator Status (ACSTAT). The internal reference is configured through one control register, Analog Comparator Reference Voltage Control (ACREFCTL). Interrupt status and control are configured through three registers, Analog Comparator Masked Interrupt Status (ACMIS), Analog Comparator Raw Interrupt Status (ACRIS), and Analog Comparator Interrupt Enable (ACINTEN).

Typically, the comparator output is used internally to generate an interrupt as controlled by the ISEN bit in the **ACCTL** register. The output may also be used to drive one of the external pins (Cno), or generate an analog-to-digital converter (ADC) trigger.


a. The TTL designation indicates the pin has TTL-compatible voltage levels.

Important: The ASRCP bits in the ACCTL register must be set before using the analog comparators.

19.3.1 Internal Reference Programming

The structure of the internal reference is shown in Figure 19-3 on page 1222. The internal reference is controlled by a single configuration register (**ACREFCTL**).

Figure 19-3. Comparator Internal Reference Structure



Note: In the figure above, N*R represents a multiple of the R value that produces the results specified in Table 19-2 on page 1222.

The internal reference can be programmed in one of two modes (low range or high range) depending on the RNG bit in the **ACREFCTL** register. When RNG is clear, the internal reference is in high-range mode, and when RNG is set the internal reference is in low-range mode.

In each range, the internal reference, V_{IREF} , has 16 pre-programmed thresholds or step values. The threshold to be used to compare the external input voltage against is selected using the VREF field in the **ACREFCTL** register.

In the high-range mode, the V_{IREF} threshold voltages start at the ideal high-range starting voltage of $V_{DDA}/4.2$ and increase in ideal constant voltage steps of $V_{DDA}/29.4$.

In the low-range mode, the V_{IREF} threshold voltages start at 0 V and increase in ideal constant voltage steps of $V_{DDA}/22.12$. The ideal V_{IREF} step voltages for each mode and their dependence on the RNG and VREF fields are summarized in Table 19-2.

Table 19-2. Internal Reference Voltage and ACREFCTL Field Values

ACREFCTL Register		Output Reference Voltage Based on VREF Field Value
EN Bit Value	RNG Bit Value	output Reference voltage based on VREF Field Value
EN=0	RNG=X	0 V (GND) for any value of <code>VREF</code> . It is recommended that <code>RNG=1</code> and <code>VREF=0</code> to minimize noise on the reference ground.

Table 19-2. Internal Reference Voltage and ACREFCTL Field Values (continued)

ACREFCTL Register		Output Reference Voltage Based on VREF Field Value		
EN Bit Value	RNG Bit Value	Output Reference voltage based on VREF Field Value		
EN=1	RNG=0	V _{IREF} High Range: 16 voltage threshold values indexed by VREF = 0x0 0xF		
		Ideal starting voltage (VREF=0): V _{DDA} / 4.2		
		Ideal step size: V _{DDA} / 29.4		
		Ideal V_{IREF} threshold values: V_{IREF} (VREF) = V_{DDA} / 4.2 + VREF * (V_{DDA} / 29.4), for VREF = 0x0 0xF		
		For minimum and maximum V_{IREF} threshold values, see Table 19-3 on page 1223.		
	RNG=1	V _{IREF} Low Range: 16 voltage threshold values indexed by VREF = 0x0 0xF		
		Ideal starting voltage (VREF=0): 0 V		
		Ideal step size: V _{DDA} / 22.12		
		Ideal V_{IREF} threshold values: V_{IREF} (VREF) = VREF * (V_{DDA} / 22.12), for VREF = 0x0 0xF		
		For minimum and maximum V_{IREF} threshold values, see Table 19-4 on page 1224.		

Note that the values shown in Table 19-2 are the ideal values of the V_{IREF} thresholds. These values actually vary between minimum and maximum values for each threshold step, depending on process and temperature. The minimum and maximum values for each step are given by:

- V_{IREF}(VREF) [Min] = Ideal V_{IREF}(VREF) (Ideal Step size 2 mV) / 2
- V_{IREF}(VREF) [Max] = Ideal V_{IREF}(VREF) + (Ideal Step size 2 mV) / 2

Examples of minimum and maximum V_{IREF} values for V_{DDA} = 3.3V for high and low ranges, are shown in Table 19-3 and Table 19-4. Note that these examples are only valid for V_{DDA} = 3.3V; values scale up and down with V_{DDA} .

Table 19-3. Analog Comparator Voltage Reference Characteristics, V_{DDA} = 3.3V, EN= 1, and RNG = 0

VREF Value	V _{IREF} Min	Ideal V _{IREF}	V _{IREF} Max	Unit
0x0	0.731	0.786	0.841	V
0x1	0.843	0.898	0.953	V
0x2	0.955	1.010	1.065	V
0x3	1.067	1.122	1.178	V
0x4	1.180	1.235	1.290	V
0x5	1.292	1.347	1.402	V
0x6	1.404	1.459	1.514	V
0x7	1.516	1.571	1.627	V
0x8	1.629	1.684	1.739	V
0x9	1.741	1.796	1.851	V
0xA	1.853	1.908	1.963	V
0xB	1.965	2.020	2.076	V
0xC	2.078	2.133	2.188	V
0xD	2.190	2.245	2.300	V
0xE	2.302	2.357	2.412	V
0xF	2.414	2.469	2.525	V

Table 19-4. Analog Comparator Voltage Reference Characteristics, V_{DDA} = 3.3V, EN= 1, and RNG = 1

VREF Value	V _{IREF} Min	Ideal V _{IREF}	V _{IREF} Max	Unit
0x0	0.000	0.000	0.074	V
0x1	0.076	0.149	0.223	V
0x2	0.225	0.298	0.372	V
0x3	0.374	0.448	0.521	V
0x4	0.523	0.597	0.670	V
0x5	0.672	0.746	0.820	V
0x6	0.822	0.895	0.969	V
0x7	0.971	1.044	1.118	V
0x8	1.120	1.193	1.267	V
0x9	1.269	1.343	1.416	V
0xA	1.418	1.492	1.565	V
0xB	1.567	1.641	1.715	V
0xC	1.717	1.790	1.864	V
0xD	1.866	1.939	2.013	V
0xE	2.015	2.089	2.162	V
0xF	2.164	2.238	2.311	V

19.4 Initialization and Configuration

The following example shows how to configure an analog comparator to read back its output value from an internal register.

- 1. Enable the analog comparator clock by writing a value of 0x0000.0001 to the **RCGCACMP** register in the System Control module (see page 344).
- **2.** Enable the clock to the appropriate GPIO modules via the **RCGCGPIO** register (see page 330). To find out which GPIO ports to enable, refer to Table 23-5 on page 1367.
- **3.** In the GPIO module, enable the GPIO port/pin associated with the input signals as GPIO inputs. To determine which GPIO to configure, see Table 23-4 on page 1358.
- **4.** Configure the PMCn fields in the **GPIOPCTL** register to assign the analog comparator output signals to the appropriate pins (see page 688 and Table 23-5 on page 1367).
- **5.** Configure the internal voltage reference to 1.65 V by writing the **ACREFCTL** register with the value 0x0000.030C.
- **6.** Configure the comparator to use the internal voltage reference and to *not* invert the output by writing the **ACCTLn** register with the value of 0x0000.040C.
- 7. Delay for 10 µs.
- 8. Read the comparator output value by reading the ACSTATn register's OVAL value.

Change the level of the comparator negative input signal C- to see the OVAL value change.

19.5 Register Map

Table 19-5 on page 1225 lists the comparator registers. The offset listed is a hexadecimal increment to the register's address, relative to the Analog Comparator base address of 0x4003.C000. Note that the analog comparator clock must be enabled before the registers can be programmed (see page 344). There must be a delay of 3 system clocks after the analog comparator module clock is enabled before any analog comparator module registers are accessed.

Table 19-5. Analog Comparators Register Map

Offset	Name	Туре	Reset	Description	See page
0x000	ACMIS	R/W1C	0x0000.0000	Analog Comparator Masked Interrupt Status	1226
0x004	ACRIS	RO	0x0000.0000	Analog Comparator Raw Interrupt Status	1227
0x008	ACINTEN	R/W	0x0000.0000	Analog Comparator Interrupt Enable	1228
0x010	ACREFCTL	R/W	0x0000.0000	Analog Comparator Reference Voltage Control	1229
0x020	ACSTAT0	RO	0x0000.0000	Analog Comparator Status 0	1230
0x024	ACCTL0	R/W	0x0000.0000	Analog Comparator Control 0	1231
0x040	ACSTAT1	RO	0x0000.0000	Analog Comparator Status 1	1230
0x044	ACCTL1	R/W	0x0000.0000	Analog Comparator Control 1	1231
0x060	ACSTAT2	RO	0x0000.0000	Analog Comparator Status 2	1230
0x064	ACCTL2	R/W	0x0000.0000	Analog Comparator Control 2	1231
0xFC0	ACMPPP	RO	0x0007.0007	Analog Comparator Peripheral Properties	1233

19.6 Register Descriptions

The remainder of this section lists and describes the Analog Comparator registers, in numerical order by address offset.

Register 1: Analog Comparator Masked Interrupt Status (ACMIS), offset 0x000

This register provides a summary of the interrupt status (masked) of the comparators.

Analog Comparator Masked Interrupt Status (ACMIS)

IN0


0

R/W1C

0

Base 0x4003.C000 Offset 0x000

Type R/W1C, reset 0x0000.0000



			_						
Bit/Field	Name	Type	Reset	Description					
31:3	reserved	RO	0x0000.000	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.					
2	IN2	R/W1C	0	Comparator 2 Masked Interrupt Status					
				Value Description					
				0 No interrupt has occurred or the interrupt is masked.					
				1 The IN2 bits in the ACRIS register and the ACINTEN registers are set, providing an interrupt to the interrupt controller.					
				This bit is cleared by writing a 1. Clearing this bit also clears the ${\tt IN2}$ bit in the \textbf{ACRIS} register.					
1	IN1	R/W1C	0	Comparator 1 Masked Interrupt Status					
				Value Description					
				0 No interrupt has occurred or the interrupt is masked.					
				1 The IN1 bits in the ACRIS register and the ACINTEN registers are set, providing an interrupt to the interrupt controller.					
				This bit is cleared by writing a 1. Clearing this bit also clears the ${\tt IN1}$ bit in the ACRIS register.					

Value Description

Comparator 0 Masked Interrupt Status

- 0 No interrupt has occurred or the interrupt is masked.
- 1 The INO bits in the **ACRIS** register and the **ACINTEN** registers are set, providing an interrupt to the interrupt controller.

This bit is cleared by writing a 1. Clearing this bit also clears the ${\tt IN0}$ bit in the ACRIS register.


Register 2: Analog Comparator Raw Interrupt Status (ACRIS), offset 0x004

This register provides a summary of the interrupt status (raw) of the comparators. The bits in this register must be enabled to generate interrupts using the **ACINTEN** register.

Analog Comparator Raw Interrupt Status (ACRIS)

Base 0x4003.C000

Offset 0x004 Type RO, reset 0x0000.0000



Bit/Field	Name	Туре	Reset	Description				
31:3	reserved	RO	0x0000.000	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should b preserved across a read-modify-write operation.				
2	IN2	RO	0	Comparator 2 Interrupt Status				
				Value Description				
				0 An interrupt has not occurred.				
				1 Comparator 2 has generated an interrupt for an event as configured by the ISEN bit in the ACCTL2 register.				
				This bit is cleared by writing a 1 to the IN2 bit in the ACMIS register.				
1	IN1	RO	0	Comparator 1 Interrupt Status				
				Value Description				
				0 An interrupt has not occurred.				
				1 Comparator 1 has generated an interruptfor an event as configured by the ISEN bit in the ACCTL1 register.				
				This bit is cleared by writing a 1 to the IN1 bit in the ACMIS register.				
0	IN0	RO	0	Comparator 0 Interrupt Status				
				Value Description				

- 0 An interrupt has not occurred.
- 1 Comparator 0 has generated an interrupt for an event as configured by the ISEN bit in the **ACCTL0** register.

This bit is cleared by writing a 1 to the ${\tt IN0}$ bit in the ACMIS register.


Register 3: Analog Comparator Interrupt Enable (ACINTEN), offset 0x008

This register provides the interrupt enable for the comparators.

Analog Comparator Interrupt Enable (ACINTEN)

Base 0x4003.C000 Offset 0x008

Type R/W, reset 0x0000.0000



Bit/Field	Name	Type	Reset	Description					
31:3	reserved	RO	0x00	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.					
2	IN2	R/W	0	Comparator 2 Interrupt Enable					
				Value Description					
				O A comparator 2 interrupt does not affect the interrupt status.					
				1 The raw interrupt signal comparator 2 is sent to the interrupt controller.					
1	IN1	R/W	0	Comparator 1 Interrupt Enable					
				Value Description					
				O A comparator 1 interrupt does not affect the interrupt status.					
				1 The raw interrupt signal comparator 1 is sent to the interrupt controller.					
0	IN0	R/W	0	Comparator 0 Interrupt Enable					

Value Description

- 0 A comparator 0 interrupt does not affect the interrupt status.
- The raw interrupt signal comparator 0 is sent to the interrupt controller.

Register 4: Analog Comparator Reference Voltage Control (ACREFCTL), offset 0x010

This register specifies whether the resistor ladder is powered on as well as the range and tap.

Analog Comparator Reference Voltage Control (ACREFCTL)

Name


Type

Reset

Base 0x4003.C000

Bit/Field

Offset 0x010 Type R/W, reset 0x0000.0000



Description

	.,,,,	. 10001	2000p				
reserved	RO	0x0000.0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.				
EN	R/W	0	Resistor Ladder Enable				
			Value Description				
			0 The resistor ladder is unpowered.				
			Powers on the resistor ladder. The resistor ladder is connected to V_{DDA} .				
			This bit is cleared at reset so that the internal reference consumes the least amount of power if it is not used.				
RNG	R/W	0	Resistor Ladder Range				
			Value Description				
			0 The ideal step size for the internal reference is VDDA / 29.4.				
			1 The ideal step size for the internal reference is VDDA / 22.12.				
reserved	RO	0x0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.				
VREF	R/W	0x0	Resistor Ladder Voltage Ref				
			The \mathtt{VREF} bit field specifies the resistor ladder tap that is passed through				
	EN RNG reserved	EN R/W RNG R/W reserved RO	EN R/W 0 RNG R/W 0 reserved RO 0x0				

an analog multiplexer. The voltage corresponding to the tap position is the internal reference voltage available for comparison. See Table 19-2 on page 1222 for some output reference voltage examples.

Register 5: Analog Comparator Status 0 (ACSTAT0), offset 0x020

Register 6: Analog Comparator Status 1 (ACSTAT1), offset 0x040

Register 7: Analog Comparator Status 2 (ACSTAT2), offset 0x060

These registers specify the current output value of the comparator.

Analog Comparator Status n (ACSTATn)

Base 0x4003.C000 Offset 0x020

Type RO, reset 0x0000.0000

_	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16
								rese	rved							1
Type	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO
Reset	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0
	15	14	13	12	11	10	9	8	7	6	5	4	3	2	1	0
		'				reserved									OVAL	reserved
Type	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO
Reset	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0

Bit/Field	Name	Туре	Reset	Description		
31:2	reserved	RO	0x0000.000	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should preserved across a read-modify-write operation.		
1	OVAL	RO	0	Comparator Output Value		
				Value Description 0 VIN- > VIN+ 1 VIN- < VIN+ VIN - is the voltage on the Cn- pin. VIN+ is the voltage on the Cn+ pin,		
				the C0+ pin, or the internal voltage reference (V_{IREF}) as defined by the ASRCP bit in the ACCTL register.		
0	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.		

Register 8: Analog Comparator Control 0 (ACCTL0), offset 0x024 Register 9: Analog Comparator Control 1 (ACCTL1), offset 0x044 Register 10: Analog Comparator Control 2 (ACCTL2), offset 0x064

These registers configure the comparator's input and output.

Analog Comparator Control n (ACCTLn)

Base 0x4003.C000 Offset 0x024

Type R/W, reset 0x0000.0000

_	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16
		1		1	 		1	rese	rved						1	
Туре	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO
Reset	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0
_	15	14	13	12	11	10	9	8	7	6	5	4	3	2	1	0
		rese	rved	1	TOEN	ASI	RCP	reserved	TSLVAL	TS	EN	ISLVAL	IS	EN	CINV	reserved
Туре	RO	rese	rved	RO	TOEN R/W	ASI R/W	RCP R/W	reserved RO	TSLVAL R/W	TS R/W	EN R/W	ISLVAL R/W	IS R/W	EN R/W	CINV R/W	reserved
Type Reset	RO 0			RO 0												

Bit/Field	Name	Туре	Reset	Description				
31:12	reserved	RO	0x0000.0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.				
11	TOEN	R/W	0	Trigger Output Enable				
				Value Description				
				0 ADC events are suppressed and not sent to the ADC.				
				1 ADC events are sent to the ADC.				
10:9	ASRCP	R/W	0x0	Analog Source Positive				
				The ASRCP field specifies the source of input voltage to the VIN+ terminal of the comparator. The encodings for this field are as follows:				
				Value Description				
				0x0 Pin value of Cn+				
				0x1 Pin value of C0+				
				0x2 Internal voltage reference (V _{IREF})				
				0x3 Reserved				
8	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.				
7	TSLVAL	R/W	0	Trigger Sense Level Value				

Value Description

- O An ADC event is generated if the comparator output is Low.
- 1 An ADC event is generated if the comparator output is High.


Bit/Field	Name	Туре	Reset	Description					
6:5	TSEN	R/W	0x0	Trigger Sense The TSEN field specifies the sense of the comparator output that generates an ADC event. The sense conditioning is as follows:					
				Value Description					
				0x0 Level sense, see TSLVAL					
				0x1 Falling edge					
				0x2 Rising edge					
				0x3 Either edge					
4	ISLVAL	R/W	0	Interrupt Sense Level Value					
				Value Description					
				O An interrupt is generated if the comparator output is Low.					
				1 An interrupt is generated if the comparator output is High.					
3:2	ISEN	R/W	0x0	Interrupt Sense					
				The ISEN field specifies the sense of the comparator output that generates an interrupt. The sense conditioning is as follows:					
				Value Description					
				0x0 Level sense, see ISLVAL					
				0x1 Falling edge					
				0x2 Rising edge					
				0x3 Either edge					
1	CINV	R/W	0	Comparator Output Invert					
				Value Description					
				The output of the comparator is unchanged.					
				The output of the comparator is inverted prior to being processed by hardware.					
0	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.					

Register 11: Analog Comparator Peripheral Properties (ACMPPP), offset 0xFC0

The **ACMPPP** register provides information regarding the properties of the analog comparator module.

Analog Comparator Peripheral Properties (ACMPPP)

Base 0x4003.C000 Offset 0xFC0 Type RO, reset 0x0007.0007



Bit/Field	Name	Туре	Reset	Description					
31:19	reserved	RO	0x0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.					
18	C2O	RO	0x1	Comparator Output 2 Present					
				Value Description					
				O Comparator output 2 is not present.					
				1 Comparator output 2 is present.					
17	C10	RO	0x1	Comparator Output 1 Present					
				Value Description					
				O Comparator output 1 is not present.					
				1 Comparator output 1 is present.					
16	C0O	RO	0x1	Comparator Output 0 Present					
				Value Description					
				0 Comparator output 0 is not present.					
				1 Comparator output 0 is present.					
15:3	reserved	RO	0x0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.					
2	CMP2	RO	0x1	Comparator 2 Present					
				Value Description					

0 Comparator 2 is not present.

Comparator 2 is present.

Bit/Field	Name	Type	Reset	Description
1	CMP1	RO	0x1	Comparator 1 Present
				Value Description
				 Comparator 1 is not present.
				1 Comparator 1 is present.
0	CMP0	RO	0x1	Comparator 0 Present
U	CIVIFO	KO	UXI	Comparator o Fresent
				Value Description
				0 Comparator 0 is not present.
				1 Comparator 0 is present.

20 Pulse Width Modulator (PWM)

Pulse width modulation (PWM) is a powerful technique for digitally encoding analog signal levels. High-resolution counters are used to generate a square wave, and the duty cycle of the square wave is modulated to encode an analog signal. Typical applications include switching power supplies and motor control.

The Stellaris[®] microcontroller contains two PWM modules, each with four PWM generator blocks and a control block, for a total of 16 PWM outputs. The control block determines the polarity of the PWM signals, and which signals are passed through to the pins.

Each PWM generator block produces two PWM signals that share the same timer and frequency and can either be programmed with independent actions or as a single pair of complementary signals with dead-band delays inserted. The output signals, pwmA' and pwmB', of the PWM generation blocks are managed by the output control block before being passed to the device pins as MnPWM0 and MnPWM1 or MnPWM2 and MnPWM3, and so on.

Each Stellaris PWM module provides a great deal of flexibility and can generate simple PWM signals, such as those required by a simple charge pump as well as paired PWM signals with dead-band delays, such as those required by a half-H bridge driver. Three generator blocks can also generate the full six channels of gate controls required by a 3-phase inverter bridge.

Each PWM generator block has the following features:

- Four fault-condition handling inputs to quickly provide low-latency shutdown and prevent damage to the motor being controlled, for a total of eight inputs
- One 16-bit counter
 - Runs in Down or Up/Down mode
 - Output frequency controlled by a 16-bit load value
 - Load value updates can be synchronized
 - Produces output signals at zero and load value
- Two PWM comparators
 - Comparator value updates can be synchronized
 - Produces output signals on match
- PWM signal generator
 - Output PWM signal is constructed based on actions taken as a result of the counter and PWM comparator output signals
 - Produces two independent PWM signals
- Dead-band generator
 - Produces two PWM signals with programmable dead-band delays suitable for driving a half-H bridge
 - Can be bypassed, leaving input PWM signals unmodified

■ Can initiate an ADC sample sequence

The control block determines the polarity of the PWM signals and which signals are passed through to the pins. The output of the PWM generation blocks are managed by the output control block before being passed to the device pins. The PWM control block has the following options:

- PWM output enable of each PWM signal
- Optional output inversion of each PWM signal (polarity control)
- Optional fault handling for each PWM signal
- Synchronization of timers in the PWM generator blocks
- Synchronization of timer/comparator updates across the PWM generator blocks
- Extended PWM synchronization of timer/comparator updates across the PWM generator blocks
- Interrupt status summary of the PWM generator blocks
- Extended PWM fault handling, with multiple fault signals, programmable polarities, and filtering
- PWM generators can be operated independently or synchronized with other generators

20.1 Block Diagram

Figure 20-1 on page 1237 provides the Stellaris PWM module diagram and Figure 20-2 on page 1237 provides a more detailed diagram of a Stellaris PWM generator. The LM4F232H5QC controller contains two PWM modules, each with four generator blocks that generate eight independent PWM signals or four paired PWM signals with dead-band delays inserted.





Figure 20-1. PWM Module Diagram

Figure 20-2. PWM Generator Block Diagram



20.2 Signal Description

The following table lists the external signals of the PWM modules and describes the function of each. The PWM controller signals are alternate functions for some GPIO signals and default to be

GPIO signals at reset. The column in the table below titled "Pin Mux/Pin Assignment" lists the possible GPIO pin placements for these PWM signals. The AFSEL bit in the GPIO Alternate Function Select (GPIOAFSEL) register (page 670) should be set to choose the PWM function. The number in parentheses is the encoding that must be programmed into the PMCn field in the GPIO Port Control (GPIOPCTL) register (page 688) to assign the PWM signal to the specified GPIO port pin. For more information on configuring GPIOs, see "General-Purpose Input/Outputs (GPIOs)" on page 646.

Table 20-1. PWM Signals (100LQFP)

Pin Name	Pin Number	Pin Mux / Pin Assignment	Pin Type	Buffer Type ^a	Description
M0FAULT0	3 16 42 99	PD2 (4) PH0 (6) PF2 (4) PD6 (4)	I	TTL	Motion Control Module 0 PWM Fault 0.
M0FAULT1	17 43 60 100	PH1 (6) PF3 (4) PG2 (4) PD7 (4)	ı	TTL	Motion Control Module 0 PWM Fault 1.
M0FAULT2	18 39 59	PH2 (6) PF4 (4) PG3 (4)	I	TTL	Motion Control Module 0 PWM Fault 2.
M0FAULT3	19 37	PH3 (6) PF5 (4)	I	TTL	Motion Control Module 0 PWM Fault 3.
M0PWM0	16	PH0 (4)	0	TTL	Motion Control Module 0 PWM 0. This signal is controlled by Module 0 PWM Generator 0.
M0PWM1	17	PH1 (4)	0	TTL	Motion Control Module 0 PWM 1. This signal is controlled by Module 0 PWM Generator 0.
MOPWM2	18 92	PH2 (4) PB4 (4)	0	TTL	Motion Control Module 0 PWM 2. This signal is controlled by Module 0 PWM Generator 1.
MOPWM3	19 91	PH3 (4) PB5 (4)	0	TTL	Motion Control Module 0 PWM 3. This signal is controlled by Module 0 PWM Generator 1.
M0PWM4	74 79 95	PG4 (4) PH4 (4) PE4 (4)	0	TTL	Motion Control Module 0 PWM 4. This signal is controlled by Module 0 PWM Generator 2.
M0PWM5	75 78 96	PG5 (4) PH5 (4) PE5 (4)	0	TTL	Motion Control Module 0 PWM 5. This signal is controlled by Module 0 PWM Generator 2.
M0PWM6	1 25 77 87	PD0 (4) PC4 (4) PH6 (4) PG6 (4)	0	TTL	Motion Control Module 0 PWM 6. This signal is controlled by Module 0 PWM Generator 3.
M0PWM7	2 24 76 88	PD1 (4) PC5 (4) PH7 (4) PG7 (4)	0	TTL	Motion Control Module 0 PWM 7. This signal is controlled by Module 0 PWM Generator 3.
M1FAULT0	39 49 58	PF4 (5) PK0 (6) PF7 (5)	1	TTL	Motion Control Module 1 PWM Fault 0.
M1FAULT1	48 62	PK1 (6) PG0 (5)	1	TTL	Motion Control Module 1 PWM Fault 1.
M1FAULT2	47 61	PK2 (6) PG1 (5)	I	TTL	Motion Control Module 1 PWM Fault 2.

Table 20-1. PWM Signals (100LQFP) (continued)

Pin Name	Pin Number	Pin Mux / Pin Assignment	Pin Type	Buffer Type ^a	Description
M1FAULT3	46	PK3 (6)	1	TTL	Motion Control Module 1 PWM Fault 3.
M1PWM0	1 60	PD0 (5) PG2 (5)	0	TTL	Motion Control Module 1 PWM 0. This signal is controlled by Module 1 PWM Generator 0.
M1PWM1	2 59	PD1 (5) PG3 (5)	0	TTL	Motion Control Module 1 PWM 1. This signal is controlled by Module 1 PWM Generator 0.
M1PWM2	34 74 95	PA6 (5) PG4 (5) PE4 (5)	0	TTL	Motion Control Module 1 PWM 2. This signal is controlled by Module 1 PWM Generator 1.
M1PWM3	35 75 96	PA7 (5) PG5 (5) PE5 (5)	0	TTL	Motion Control Module 1 PWM 3. This signal is controlled by Module 1 PWM Generator 1.
M1PWM4	40	PF0 (5)	0	TTL	Motion Control Module 1 PWM 4. This signal is controlled by Module 1 PWM Generator 2.
M1PWM5	41	PF1 (5)	0	TTL	Motion Control Module 1 PWM 5. This signal is controlled by Module 1 PWM Generator 2.
M1PWM6	42	PF2 (5)	0	TTL	Motion Control Module 1 PWM 6. This signal is controlled by Module 1 PWM Generator 3.
M1PWM7	43	PF3 (5)	0	TTL	Motion Control Module 1 PWM 7. This signal is controlled by Module 1 PWM Generator 3.

a. The TTL designation indicates the pin has TTL-compatible voltage levels.

20.3 Functional Description

20.3.1 **PWM Timer**

The timer in each PWM generator runs in one of two modes: Count-Down mode or Count-Up/Down mode. In Count-Down mode, the timer counts from the load value to zero, goes back to the load value, and continues counting down. In Count-Up/Down mode, the timer counts from zero up to the load value, back down to zero, back up to the load value, and so on. Generally, Count-Down mode is used for generating left- or right-aligned PWM signals, while the Count-Up/Down mode is used for generating center-aligned PWM signals.

The timers output three signals that are used in the PWM generation process: the direction signal (this is always Low in Count-Down mode, but alternates between Low and High in Count-Up/Down mode), a single-clock-cycle-width High pulse when the counter is zero, and a single-clock-cycle-width High pulse when the counter is equal to the load value. Note that in Count-Down mode, the zero pulse is immediately followed by the load pulse. In the figures in this chapter, these signals are labelled "dir," "zero," and "load."

20.3.2 PWM Comparators


Each PWM generator has two comparators that monitor the value of the counter; when either comparator matches the counter, they output a single-clock-cycle-width High pulse, labelled "cmpA" and "cmpB" in the figures in this chapter. When in Count-Up/Down mode, these comparators match both when counting up and when counting down, and thus are qualified by the counter direction signal. These qualified pulses are used in the PWM generation process. If either comparator match value is greater than the counter load value, then that comparator never outputs a High pulse.

Figure 20-3 on page 1240 shows the behavior of the counter and the relationship of these pulses when the counter is in Count-Down mode. Figure 20-4 on page 1241 shows the behavior of the counter

and the relationship of these pulses when the counter is in Count-Up/Down mode. In these figures, the following definitions apply:

- LOAD is the value in the **PWMnLOAD** register
- COMPA is the value in the PWMnCMPA register
- COMPB is the value in the PWMnCMPB register
- 0 is the value zero
- load is the internal signal that has a single-clock-cycle-width High pulse when the counter is equal to the load value
- zero is the internal signal that has a single-clock-cycle-width High pulse when the counter is zero
- cmpA is the internal signal that has a single-clock-cycle-width High pulse when the counter is equal to COMPA
- cmpB is the internal signal that has a single-clock-cycle-width High pulse when the counter is equal to COMPB
- dir is the internal signal that indicates the count direction

Figure 20-3. PWM Count-Down Mode






Figure 20-4. PWM Count-Up/Down Mode

20.3.3 PWM Signal Generator

Each PWM generator takes the load, zero, cmpA, and cmpB pulses (qualified by the dir signal) and generates two internal PWM signals, pwmA and pwmB. In Count-Down mode, there are four events that can affect these signals: zero, load, match A down, and match B down. In Count-Up/Down mode, there are six events that can affect these signals: zero, load, match A down, match A up, match B down, and match B up. The match A or match B events are ignored when they coincide with the zero or load events. If the match A and match B events coincide, the first signal, pwmA, is generated based only on the match A event, and the second signal, pwmB, is generated based only on the match B event.

For each event, the effect on each output PWM signal is programmable: it can be left alone (ignoring the event), it can be toggled, it can be driven Low, or it can be driven High. These actions can be used to generate a pair of PWM signals of various positions and duty cycles, which do or do not overlap. Figure 20-5 on page 1241 shows the use of Count-Up/Down mode to generate a pair of center-aligned, overlapped PWM signals that have different duty cycles. This figure shows the pwmA and pwmB signals before they have passed through the dead-band generator.




Figure 20-5. PWM Generation Example In Count-Up/Down Mode

In this example, the first generator is set to drive High on match A up, drive Low on match A down, and ignore the other four events. The second generator is set to drive High on match B up, drive Low on match B down, and ignore the other four events. Changing the value of comparator A changes the duty cycle of the pwmA signal, and changing the value of comparator B changes the duty cycle of the pwmB signal.


February 20, 2013 1241

20.3.4 Dead-Band Generator

The pwmA and pwmB signals produced by each PWM generator are passed to the dead-band generator. If the dead-band generator is disabled, the PWM signals simply pass through to the pwmA' and pwmB' signals unmodified. If the dead-band generator is enabled, the pwmB signal is lost and two PWM signals are generated based on the pwmA signal. The first output PWM signal, pwmA' is the pwmA signal with the rising edge delayed by a programmable amount. The second output PWM signal, pwmB', is the inversion of the pwmA signal with a programmable delay added between the falling edge of the pwmA signal and the rising edge of the pwmB' signal.

The resulting signals are a pair of active High signals where one is always High, except for a programmable amount of time at transitions where both are Low. These signals are therefore suitable for driving a half-H bridge, with the dead-band delays preventing shoot-through current from damaging the power electronics. Figure 20-6 on page 1242 shows the effect of the dead-band generator on the pwmA signal and the resulting pwmA' and pwmB' signals that are transmitted to the output control block.

Figure 20-6. PWM Dead-Band Generator



20.3.5 Interrupt/ADC-Trigger Selector

Each PWM generator also takes the same four (or six) counter events and uses them to generate an interrupt or an ADC trigger. Any of these events or a set of these events can be selected as a source for an interrupt; when any of the selected events occur, an interrupt is generated. Additionally, the same event, a different event, the same set of events, or a different set of events can be selected as a source for an ADC trigger; when any of these selected events occur, an ADC trigger pulse is generated. The selection of events allows the interrupt or ADC trigger to occur at a specific position within the pwmA or pwmB signal. Note that interrupts and ADC triggers are based on the raw events; delays in the PWM signal edges caused by the dead-band generator are not taken into account.

20.3.6 Synchronization Methods

Each PWM module provides four PWM generators, each providing two PWM outputs that may be used in a wide variety of applications. Generally speaking, the PWM is used in one of two categories of operation:

- **Unsynchronized.** The PWM generator and its two output signals are used alone, independent of other PWM generators.
- **Synchronized.** The PWM generator and its two outputs signals are used in conjunction with other PWM generators using a common, unified time base. If multiple PWM generators are configured with the same counter load value, synchronization can be used to guarantee that they also have the same count value (the PWM generators must be configured before they are synchronized). With this feature, more than two MnPWMn signals can be produced with a known relationship between the edges of those signals because the counters always have the same

values. Other states in the module provide mechanisms to maintain the common time base and mutual synchronization.

The counter in a PWM generator can be reset to zero by writing the **PWM Time Base Sync** (**PWMSYNC**) register and setting the SYNCn bit associated with the generator. Multiple PWM generators can be synchronized together by setting all necessary SYNCn bits in one access. For example, setting the SYNC0 and SYNC1 bits in the **PWMSYNC** register causes the counters in PWM generators 0 and 1 to reset together.

Additional synchronization can occur between multiple PWM generators by updating register contents in one of the following three ways:

- Immediately. The write value has immediate effect, and the hardware reacts immediately.
- Locally Synchronized. The write value does not affect the logic until the counter reaches the value zero at the end of the PWM cycle. In this case, the effect of the write is deferred, providing a guaranteed defined behavior and preventing overly short or overly long output PWM pulses.
- Globally Synchronized. The write value does not affect the logic until two sequential events have occurred: (1) the Update mode for the generator function is programmed for global synchronization in the PWMnCTL register, and (2) the counter reaches zero at the end of the PWM cycle. In this case, the effect of the write is deferred until the end of the PWM cycle following the end of all updates. This mode allows multiple items in multiple PWM generators to be updated simultaneously without odd effects during the update; everything runs from the old values until a point at which they all run from the new values. The Update mode of the load and comparator match values can be individually configured in each PWM generator block. It typically makes sense to use the synchronous update mechanism across PWM generator blocks when the timers in those blocks are synchronized, although this is not required in order for this mechanism to function properly.

The following registers provide either local or global synchronization based on the state of various Update mode bits and fields in the **PWMnCTL** register (LOADUPD; CMPAUPD):

■ Generator Registers: PWMnLOAD, PWMnCMPA, and PWMnCMPB

The following registers default to immediate update, but are provided with the optional functionality of synchronously updating rather than having all updates take immediate effect:

- Module-Level Register: PWMENABLE (based on the state of the ENUPDn bits in the PWMENUPD register).
- Generator Register: PWMnGENA, PWMnGENB, PWMnDBCTL, PWMnDBRISE, and PWMnDBFALL (based on the state of various Update mode bits and fields in the PWMnCTL register (GENAUPD; GENBUPD; DBCTLUPD; DBRISEUPD; DBFALLUPD)).

All other registers are considered statically provisioned for the execution of an application or are used dynamically for purposes unrelated to maintaining synchronization and therefore do not need synchronous update functionality.

20.3.7 Fault Conditions

A fault condition is one in which the controller must be signaled to stop normal PWM function and then set the MnPWMn signals to a safe state. Two basic situations cause fault conditions:

- The microcontroller is stalled and cannot perform the necessary computation in the time required for motion control
- An external error or event is detected

Each PWM generator can use the following inputs to generate a fault condition, including:

- MnfAULTn pin assertion
- A stall of the controller generated by the debugger
- The trigger of an ADC digital comparator

Fault conditions are calculated on a per-PWM generator basis. Each PWM generator configures the necessary conditions to indicate a fault condition exists. This method allows the development of applications with dependent and independent control.

Eight fault input pins (MnFAULTn) are available. These inputs may be used with circuits that generate an active High or active Low signal to indicate an error condition. A MnFAULTn pins may be individually programmed for the appropriate logic sense using the **PWMnFLTSEN** register.

The PWM generator's mode control, including fault condition handling, is provided in the **PWMnCTL** register. The **PWMnCTL** register also selects whether the fault condition is maintained as long as the external condition lasts or if it is latched until the fault condition until cleared by software. Finally, this register also enables a counter that may be used to extend the period of a fault condition for external events to assure that the duration is a minimum length. The minimum fault period count is specified in the **PWMnMINFLTPER** register.

Status regarding the specific fault cause is provided in the **PWMnFLTSTAT0** and **PWMnFLTSTAT1** registers.

PWM generator fault conditions may be promoted to a controller interrupt using the **PWMINTEN** register.

20.3.8 Output Control Block

The output control block takes care of the final conditioning of the pwmA' and pwmB' signals before they go to the pins as the MnPWMn signals. Via a single register, the **PWM Output Enable** (**PWNENABLE**) register, the set of PWM signals that are actually enabled to the pins can be modified. This function can be used, for example, to perform commutation of a brushless DC motor with a single register write (and without modifying the individual PWM generators, which are modified by the feedback control loop). In addition, the updating of the bits in the **PWMENABLE** register can be configured to be immediate or locally or globally synchronized to the next synchronous update using the **PWM Enable Update (PWMENUPD)** register.

During fault conditions, the PWM output signals, MnPWMn, usually must be driven to safe values so that external equipment may be safely controlled. The **PWMFAULT** register specifies whether during a fault condition, the generated signal continues to be passed driven or to an encoding specified in the **PWMFAULTVAL** register.

A final inversion can be applied to any of the MnPWMn signals, making them active Low instead of the default active High using the **PWM Output Inversion (PWMINVERT)**. The inversion is applied even if a value has been enabled in the **PWMFAULT** register and specified in the **PWMFAULTVAL** register. In other words, if a bit is set in the **PWMFAULT, PWMFAULTVAL**, and **PWMINVERT** registers, the output on the MnPWMn signal is 0, not 1 as specified in the **PWMFAULTVAL** register.

20.4 Initialization and Configuration

The following example shows how to initialize PWM Generator 0 with a 25-kHz frequency, a 25% duty cycle on the MnPWM0 pin, and a 75% duty cycle on the MnPWM1 pin. This example assumes the system clock is 20 MHz.

- **1.** Enable the PWM clock by writing a value of 0x0010.0000 to the **RCGC0** register in the System Control module (see page 449).
- 2. Enable the clock to the appropriate GPIO module via the RCGC2 register in the System Control module (see page 457).
- 3. In the GPIO module, enable the appropriate pins for their alternate function using the **GPIOAFSEL** register. To determine which GPIOs to configure, see Table 23-4 on page 1358.
- **4.** Configure the PMCn fields in the **GPIOPCTL** register to assign the PWM signals to the appropriate pins (see page 688 and Table 23-5 on page 1367).
- 5. Configure the Run-Mode Clock Configuration (RCC) register in the System Control module to use the PWM divide (USEPWMDIV) and set the divider (PWMDIV) to divide by 2 (000).
- 6. Configure the PWM generator for countdown mode with immediate updates to the parameters.
 - Write the **PWM0CTL** register with a value of 0x0000.0000.
 - Write the **PWM0GENA** register with a value of 0x0000.008C.
 - Write the **PWM0GENB** register with a value of 0x0000.080C.
- 7. Set the period. For a 25-KHz frequency, the period = 1/25,000, or 40 microseconds. The PWM clock source is 10 MHz; the system clock divided by 2. Thus there are 400 clock ticks per period. Use this value to set the PWM0LOAD register. In Count-Down mode, set the LOAD field in the PWM0LOAD register to the requested period minus one.
 - Write the **PWM0LOAD** register with a value of 0x0000.018F.
- 8. Set the pulse width of the MnPWM0 pin for a 25% duty cycle.
 - Write the **PWM0CMPA** register with a value of 0x0000.012B.
- 9. Set the pulse width of the MnPWM1 pin for a 75% duty cycle.
 - Write the **PWM0CMPB** register with a value of 0x0000.0063.
- **10.** Start the timers in PWM generator 0.
 - Write the **PWM0CTL** register with a value of 0x0000.0001.
- **11.** Enable PWM outputs.
 - Write the **PWMENABLE** register with a value of 0x0000.0003.

20.5 Register Map

Table 20-2 on page 1246 lists the PWM registers. The offset listed is a hexadecimal increment to the register's address, relative to the PWM module's base address:

■ PWM0: 0x4002.8000

■ PWM1: 0x4002.9000

Note that the PWM module clock must be enabled before the registers can be programmed (see page 449). There must be a delay of 3 system clocks after the PWM module clock is enabled before any PWM module registers are accessed.

Table 20-2. PWM Register Map

Offset	Name	Туре	Reset	Description	See page
0x000	PWMCTL	R/W	0x0000.0000	PWM Master Control	1249
0x004	PWMSYNC	R/W	0x0000.0000	PWM Time Base Sync	1251
0x008	PWMENABLE	R/W	0x0000.0000	PWM Output Enable	1252
0x00C	PWMINVERT	R/W	0x0000.0000	PWM Output Inversion	1254
0x010	PWMFAULT	R/W	0x0000.0000	PWM Output Fault	1256
0x014	PWMINTEN	R/W	0x0000.0000	PWM Interrupt Enable	1258
0x018	PWMRIS	RO	0x0000.0000	PWM Raw Interrupt Status	1260
0x01C	PWMISC	R/W1C	0x0000.0000	PWM Interrupt Status and Clear	1263
0x020	PWMSTATUS	RO	0x0000.0000	PWM Status	1266
0x024	PWMFAULTVAL	R/W	0x0000.0000	PWM Fault Condition Value	1268
0x028	PWMENUPD	R/W	0x0000.0000	PWM Enable Update	1270
0x040	PWM0CTL	R/W	0x0000.0000	PWM0 Control	1274
0x044	PWM0INTEN	R/W	0x0000.0000	PWM0 Interrupt and Trigger Enable	1279
0x048	PWM0RIS	RO	0x0000.0000	PWM0 Raw Interrupt Status	1282
0x04C	PWM0ISC	R/W1C	0x0000.0000	PWM0 Interrupt Status and Clear	1284
0x050	PWM0LOAD	R/W	0x0000.0000	PWM0 Load	1286
0x054	PWM0COUNT	RO	0x0000.0000	PWM0 Counter	1287
0x058	PWM0CMPA	R/W	0x0000.0000	PWM0 Compare A	1288
0x05C	PWM0CMPB	R/W	0x0000.0000	PWM0 Compare B	1289
0x060	PWM0GENA	R/W	0x0000.0000	PWM0 Generator A Control	1290
0x064	PWM0GENB	R/W	0x0000.0000	PWM0 Generator B Control	1293
0x068	PWM0DBCTL	R/W	0x0000.0000	PWM0 Dead-Band Control	1296
0x06C	PWM0DBRISE	R/W	0x0000.0000	PWM0 Dead-Band Rising-Edge Delay	1297
0x070	PWM0DBFALL	R/W	0x0000.0000	PWM0 Dead-Band Falling-Edge-Delay	1298
0x074	PWM0FLTSRC0	R/W	0x0000.0000	PWM0 Fault Source 0	1299
0x078	PWM0FLTSRC1	R/W	0x0000.0000	PWM0 Fault Source 1	1301
0x07C	PWM0MINFLTPER	R/W	0x0000.0000	PWM0 Minimum Fault Period	1304

Table 20-2. PWM Register Map (continued)

Offset	Name	Туре	Reset	Description	See page
0x080	PWM1CTL	R/W	0x0000.0000	PWM1 Control	1274
0x084	PWM1INTEN	R/W	0x0000.0000	PWM1 Interrupt and Trigger Enable	1279
0x088	PWM1RIS	RO	0x0000.0000	PWM1 Raw Interrupt Status	1282
0x08C	PWM1ISC	R/W1C	0x0000.0000	PWM1 Interrupt Status and Clear	1284
0x090	PWM1LOAD	R/W	0x0000.0000	PWM1 Load	1286
0x094	PWM1COUNT	RO	0x0000.0000	PWM1 Counter	1287
0x098	PWM1CMPA	R/W	0x0000.0000	PWM1 Compare A	1288
0x09C	PWM1CMPB	R/W	0x0000.0000	PWM1 Compare B	1289
0x0A0	PWM1GENA	R/W	0x0000.0000	PWM1 Generator A Control	1290
0x0A4	PWM1GENB	R/W	0x0000.0000	PWM1 Generator B Control	1293
0x0A8	PWM1DBCTL	R/W	0x0000.0000	PWM1 Dead-Band Control	1296
0x0AC	PWM1DBRISE	R/W	0x0000.0000	PWM1 Dead-Band Rising-Edge Delay	1297
0x0B0	PWM1DBFALL	R/W	0x0000.0000	PWM1 Dead-Band Falling-Edge-Delay	1298
0x0B4	PWM1FLTSRC0	R/W	0x0000.0000	PWM1 Fault Source 0	1299
0x0B8	PWM1FLTSRC1	R/W	0x0000.0000	PWM1 Fault Source 1	1301
0x0BC	PWM1MINFLTPER	R/W	0x0000.0000	PWM1 Minimum Fault Period	1304
0x0C0	PWM2CTL	R/W	0x0000.0000	PWM2 Control	1274
0x0C4	PWM2INTEN	R/W	0x0000.0000	PWM2 Interrupt and Trigger Enable	1279
0x0C8	PWM2RIS	RO	0x0000.0000	PWM2 Raw Interrupt Status	1282
0x0CC	PWM2ISC	R/W1C	0x0000.0000	PWM2 Interrupt Status and Clear	1284
0x0D0	PWM2LOAD	R/W	0x0000.0000	PWM2 Load	1286
0x0D4	PWM2COUNT	RO	0x0000.0000	PWM2 Counter	1287
0x0D8	PWM2CMPA	R/W	0x0000.0000	PWM2 Compare A	1288
0x0DC	PWM2CMPB	R/W	0x0000.0000	PWM2 Compare B	1289
0x0E0	PWM2GENA	R/W	0x0000.0000	PWM2 Generator A Control	1290
0x0E4	PWM2GENB	R/W	0x0000.0000	PWM2 Generator B Control	1293
0x0E8	PWM2DBCTL	R/W	0x0000.0000	PWM2 Dead-Band Control	1296
0x0EC	PWM2DBRISE	R/W	0x0000.0000	PWM2 Dead-Band Rising-Edge Delay	1297
0x0F0	PWM2DBFALL	R/W	0x0000.0000	PWM2 Dead-Band Falling-Edge-Delay	1298
0x0F4	PWM2FLTSRC0	R/W	0x0000.0000	PWM2 Fault Source 0	1299
0x0F8	PWM2FLTSRC1	R/W	0x0000.0000	PWM2 Fault Source 1	1301
0x0FC	PWM2MINFLTPER	R/W	0x0000.0000	PWM2 Minimum Fault Period	1304

Table 20-2. PWM Register Map (continued)

Offset	Name	Туре	Reset	Description	See page
0x100	PWM3CTL	R/W	0x0000.0000	PWM3 Control	1274
0x104	PWM3INTEN	R/W	0x0000.0000	PWM3 Interrupt and Trigger Enable	1279
0x108	PWM3RIS	RO	0x0000.0000	PWM3 Raw Interrupt Status	1282
0x10C	PWM3ISC	R/W1C	0x0000.0000	PWM3 Interrupt Status and Clear	1284
0x110	PWM3LOAD	R/W	0x0000.0000	PWM3 Load	1286
0x114	PWM3COUNT	RO	0x0000.0000	PWM3 Counter	1287
0x118	PWM3CMPA	R/W	0x0000.0000	PWM3 Compare A	1288
0x11C	PWM3CMPB	R/W	0x0000.0000	PWM3 Compare B	1289
0x120	PWM3GENA	R/W	0x0000.0000	PWM3 Generator A Control	1290
0x124	PWM3GENB	R/W	0x0000.0000	PWM3 Generator B Control	1293
0x128	PWM3DBCTL	R/W	0x0000.0000	PWM3 Dead-Band Control	1296
0x12C	PWM3DBRISE	R/W	0x0000.0000	PWM3 Dead-Band Rising-Edge Delay	1297
0x130	PWM3DBFALL	R/W	0x0000.0000	PWM3 Dead-Band Falling-Edge-Delay	1298
0x134	PWM3FLTSRC0	R/W	0x0000.0000	PWM3 Fault Source 0	1299
0x138	PWM3FLTSRC1	R/W	0x0000.0000	PWM3 Fault Source 1	1301
0x13C	PWM3MINFLTPER	R/W	0x0000.0000	PWM3 Minimum Fault Period	1304
0x800	PWM0FLTSEN	R/W	0x0000.0000	PWM0 Fault Pin Logic Sense	1305
0x804	PWM0FLTSTAT0	-	0x0000.0000	PWM0 Fault Status 0	1306
0x808	PWM0FLTSTAT1	-	0x0000.0000	PWM0 Fault Status 1	1308
0x880	PWM1FLTSEN	R/W	0x0000.0000	PWM1 Fault Pin Logic Sense	1305
0x884	PWM1FLTSTAT0	-	0x0000.0000	PWM1 Fault Status 0	1306
0x888	PWM1FLTSTAT1	-	0x0000.0000	PWM1 Fault Status 1	1308
0x900	PWM2FLTSEN	R/W	0x0000.0000	PWM2 Fault Pin Logic Sense	1305
0x904	PWM2FLTSTAT0	-	0x0000.0000	PWM2 Fault Status 0	1306
0x908	PWM2FLTSTAT1	-	0x0000.0000	PWM2 Fault Status 1	1308
0x980	PWM3FLTSEN	R/W	0x0000.0000	PWM3 Fault Pin Logic Sense	1305
0x984	PWM3FLTSTAT0	-	0x0000.0000	PWM3 Fault Status 0	1306
0x988	PWM3FLTSTAT1	-	0x0000.0000	PWM3 Fault Status 1	1308
0xFC0	PWMPP	RO	0x0000.0344	PWM Peripheral Properties	1311

20.6 Register Descriptions

The remainder of this section lists and describes the PWM registers, in numerical order by address offset.


Register 1: PWM Master Control (PWMCTL), offset 0x000

This register provides master control over the PWM generation blocks.

PWM Master Control (PWMCTL)

PWM0 base: 0x4002.8000 PWM1 base: 0x4002.9000 Offset 0x000

Type R/W, reset 0x0000.0000



Bit/Field	Name	Type	Reset	Description
31:4	reserved	RO	0x0000	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
3	GLOBALSYNC3	R/W	0	Update PWM Generator 3

Value Description

0 No effect.

1 Any queued update to a load or comparator register in PWM generator 3 is applied the next time the corresponding counter becomes zero.

This bit automatically clears when the updates have completed; it cannot be cleared by software.

2 GLOBALSYNC2 R/W 0 Update PWM Generator 2

Value Description

0 No effect.

Any queued update to a load or comparator register in PWM generator 2 is applied the next time the corresponding counter becomes zero.

This bit automatically clears when the updates have completed; it cannot be cleared by software.

Bit/Field	Name	Туре	Reset	Description
1	GLOBALSYNC1	R/W	0	Update PWM Generator 1
				Value Description
				0 No effect.
				Any queued update to a load or comparator register in PWM generator 1 is applied the next time the corresponding counter becomes zero.
				This bit automatically clears when the updates have completed; it cannot be cleared by software.
0	GLOBALSYNC0	R/W	0	Update PWM Generator 0
				Value Description
				0 No effect.
				Any queued update to a load or comparator register in PWM generator 0 is applied the next time the corresponding counter becomes zero.
				This bit automatically clears when the updates have completed; it cannot

be cleared by software.


Register 2: PWM Time Base Sync (PWMSYNC), offset 0x004

This register provides a method to perform synchronization of the counters in the PWM generation blocks. Setting a bit in this register causes the specified counter to reset back to 0; setting multiple bits resets multiple counters simultaneously. The bits auto-clear after the reset has occurred; reading them back as zero indicates that the synchronization has completed.

PWM Time Base Sync (PWMSYNC)

PWM0 base: 0x4002.8000 PWM1 base: 0x4002.9000 Offset 0x004

Type R/W, reset 0x0000.0000



Bit/Field	Name	Туре	Reset	Description
31:4	reserved	RO	0x0000.000	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
3	SYNC3	R/W	0	Reset Generator 3 Counter
				Value Description
				0 No effect.
				1 Resets the PWM generator 3 counter.
2	SYNC2	R/W	0	Reset Generator 2 Counter
				Value Description
				0 No effect.
				1 Resets the PWM generator 2 counter.
1	SYNC1	R/W	0	Reset Generator 1 Counter
				Value Description
				0 No effect.
				1 Resets the PWM generator 1 counter.
0	SYNC0	R/W	0	Reset Generator 0 Counter
				Value Description
				0 No effect.
				1 Resets the PWM generator 0 counter.


Register 3: PWM Output Enable (PWMENABLE), offset 0x008

This register provides a master control of which generated pwmA' and pwmB' signals are output to the MnPWMn pins. By disabling a PWM output, the generation process can continue (for example, when the time bases are synchronized) without driving PWM signals to the pins. When bits in this register are set, the corresponding pwmA' or pwmB' signal is passed through to the output stage. When bits are clear, the pwmA' or pwmB' signal is replaced by a zero value which is also passed to the output stage. The **PWMINVERT** register controls the output stage, so if the corresponding bit is set in that register, the value seen on the MnPWMn signal is inverted from what is configured by the bits in this register. Updates to the bits in this register can be immediate or locally or globally synchronized to the next synchronous update as controlled by the ENUPDn fields in the **PWMENUPD** register.

PWM Output Enable (PWMENABLE)

PWM0 base: 0x4002.8000 PWM1 base: 0x4002.9000

Offset 0x008 Type R/W, reset 0x0000.0000



Bit/Field	Name	Туре	Reset	Description
31:8	reserved	RO	0x0000.00	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should preserved across a read-modify-write operation.
7	PWM7EN	R/W	0	мпРWM7 Output Enable
				Value Description
				0 The MnPWM7 signal has a zero value.
				1 The generated pwm3B' signal is passed to the MnPWM7 pin.
6	PWM6EN	R/W	0	MnPWM6 Output Enable
				Value Description
				0 The MnPWM6 signal has a zero value.
				1 The generated pwm3A' signal is passed to the MnPWM6 pin.
5	PWM5EN	R/W	0	MnPWM5 Output Enable
				Value Description

be

0

1

The MnPWM5 signal has a zero value.

The generated pwm2B' signal is passed to the MnPWM5 pin.

Bit/Field	Name	Туре	Reset	Description
4	PWM4EN	R/W	0	MnPWM4 Output Enable
				Value Description The MnPWM4 signal has a zero value. The generated pwm2A' signal is passed to the MnPWM4 pin.
3	PWM3EN	R/W	0	MnPWM3 Output Enable
				Value Description The MnPWM3 signal has a zero value. The generated pwm1B' signal is passed to the MnPWM3 pin.
2	PWM2EN	R/W	0	MnPWM2 Output Enable
				Value Description The MnPWM2 signal has a zero value. The generated pwm1A' signal is passed to the MnPWM2 pin.
1	PWM1EN	R/W	0	MnPWM1 Output Enable Value Description 0 The MnPWM1 signal has a zero value. 1 The generated pwm0B' signal is passed to the MnPWM1 pin.
0	PWM0EN	R/W	0	MnPWM0 Output Enable Value Description 0 The MnPWM0 signal has a zero value. 1 The generated pwm0A' signal is passed to the MnPWM0 pin.

February 20, 2013 1253

Register 4: PWM Output Inversion (PWMINVERT), offset 0x00C

This register provides a master control of the polarity of the MnPWMn signals on the device pins. The pwmA' and pwmB' signals generated by the PWM generator are active High; but can be made active Low via this register. Disabled PWM channels are also passed through the output inverter (if so configured) so that inactive signals can be High. In addition, if the **PWMFAULT** register enables a specific value to be placed on the MnPWMn signals during a fault condition, that value is inverted if the corresponding bit in this register is set.

PWM Output Inversion (PWMINVERT)

PWM0 base: 0x4002.8000 PWM1 base: 0x4002.9000 Offset 0x00C

Type R/W, reset 0x0000.0000

_	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16
		1			i			rese	erved •							
Type	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO
Reset	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0
_	15	14	13	12	11	10	9	8	7	6	5	4	3	2	1	0
		1	•	rese	rved				PWM7INV	PWM6INV	PWM5INV	PWM4INV	PWM3INV	PWM2INV	PWM1INV	PWM0INV
Туре	RO	RO	RO	RO	RO	RO	RO	RO	R/W	R/W	R/W	R/W	R/W	R/W	R/W	R/W
Reset	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0

Bit/Field	Name	Туре	Reset	Description
31:8	reserved	RO	0x0000.00	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
7	PWM7INV	R/W	0	Invert MnPWM7 Signal
				Value Description
				0 The MnPWM7 signal is not inverted.
				1 The MnPWM7 signal is inverted.
6	PWM6INV	R/W	0	Invert MnPWM6 Signal
				Value Description
				The MnPWM6 signal is not inverted.
				1 The MnPWM6 signal is inverted.
5	PWM5INV	R/W	0	Invert MnPWM5 Signal
				Value Description
				0 The MnPWM5 signal is not inverted.
				1 The мnРwм5 signal is inverted.
4	PWM4INV	R/W	0	Invert MnPWM4 Signal
				Value Description
				0 The MnPWM4 signal is not inverted.
				1 The MnPWM4 signal is inverted.

Bit/Field	Name	Туре	Reset	Description
3	PWM3INV	R/W	0	Invert MnPWM3 Signal
				Value Description The MnPWM3 signal is not inverted. The MnPWM3 signal is inverted.
2	PWM2INV	R/W	0	Invert MnPWM2 Signal Value Description The MnPWM2 signal is not inverted. The MnPWM2 signal is inverted.
1	PWM1INV	R/W	0	Invert MnPWM1 Signal Value Description 0 The MnPWM1 signal is not inverted. 1 The MnPWM1 signal is inverted.
0	PWMOINV	R/W	0	Invert MnPWM0 Signal Value Description 0 The MnPWM0 signal is not inverted. 1 The MnPWM0 signal is inverted.

February 20, 2013 1255

Register 5: PWM Output Fault (PWMFAULT), offset 0x010


This register controls the behavior of the MnPWMn outputs in the presence of fault conditions. Both the fault inputs (MnFAULTn pins and digital comparator outputs) and debug events are considered fault conditions. On a fault condition, each pwmA' or pwmB' signal can be passed through unmodified or driven to the value specified by the corresponding bit in the PWMFAULTVAL register. For outputs that are configured for pass-through, the debug event handling on the corresponding PWM generator also determines if the pwmA' or pwmB' signal continues to be generated.

Fault condition control occurs before the output inverter, so PWM signals driven to a specified value on fault are inverted if the channel is configured for inversion (therefore, the pin is driven to the logical complement of the specified value on a fault condition).

PWM Output Fault (PWMFAULT)

PWM0 base: 0x4002.8000 PWM1 base: 0x4002.9000 Offset 0x010

Type R/W, reset 0x0000.0000



Bit/Field	Name	Туре	Reset	Description
31:8	reserved	RO	0x0000.00	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
7	FAULT7	R/W	0	MnPWM7 Fault
				Value Description
				0 The generated pwm3B' signal is passed to the MnPWM7 pin.
				1 The MnPWM7 output signal is driven to the value specified by the PWM7 bit in the PWMFAULTVAL register.
6	FAULT6	R/W	0	MnPWM6 Fault
				Value Description
				0 The generated pwm3A' signal is passed to the MnPWM6 pin.
				1 The MnPWM6 output signal is driven to the value specified by the PWM6 bit in the PWMFAULTVAL register.
5	FAULT5	R/W	0	MnPWM5 Fault
				Value Description

- 0 The generated pwm2B' signal is passed to the MnPWM5 pin.
- 1 The MnPWM5 output signal is driven to the value specified by the PWM5 bit in the PWMFAULTVAL register.

Bit/Field	Name	Туре	Reset	Description
4	FAULT4	R/W	0	MnPWM4 Fault
				Value Description
				0 The generated pwm2A' signal is passed to the MnPWM4 pin.
				1 The MnPWM4 output signal is driven to the value specified by the PWM4 bit in the PWMFAULTVAL register.
3	FAULT3	R/W	0	MnPWM3 Fault
				Value Description
				0 The generated pwm1B' signal is passed to the MnPWM3 pin.
				1 The MnPWM3 output signal is driven to the value specified by the PWM3 bit in the PWMFAULTVAL register.
2	FAULT2	R/W	0	MnPWM2 Fault
				Value Description
				0 The generated pwm1A' signal is passed to the MnPWM2 pin.
				1 The MnPWM2 output signal is driven to the value specified by the PWM2 bit in the PWMFAULTVAL register.
1	FAULT1	R/W	0	MnPWM1 Fault
				Value Description
				0 The generated pwm0B' signal is passed to the MnPWM1 pin.
				1 The MnPWM1 output signal is driven to the value specified by the PWM1 bit in the PWMFAULTVAL register.
0	FAULT0	R/W	0	MnPwm0 Fault
				Value Description
				0 The generated pwm0A' signal is passed to the $MnPWM0$ pin.
				1 The MnPWM0 output signal is driven to the value specified by the PWM0 bit in the PWMFAULTVAL register.

February 20, 2013 1257

Register 6: PWM Interrupt Enable (PWMINTEN), offset 0x014

This register controls the global interrupt generation capabilities of the PWM module. The events that can cause an interrupt are the fault input and the individual interrupts from the PWM generators.

Note: The "n" in the INTFAULTn and INTPWMn bits in this register correspond to the PWM generators, not to the FAULTn signals.

PWM Interrupt Enable (PWMINTEN)

PWM0 base: 0x4002.8000 PWM1 base: 0x4002.9000 Offset 0x014

Type R/W, reset 0x0000.0000

_	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16
	,		1			rese	erved	'	INTFAULT3 INTFAULT2 INTFAULT1							
Type Reset	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	R/W 0	R/W 0	R/W 0	R/W 0
	15	14	13	12	11	10	9	8	7	6	5	4	3	2	1	0
	ı		1	1	, , ,	rese	erved	,					INTPWM3	INTPWM2	INTPWM1	INTPWM0
Type Reset	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	R/W 0	R/W 0	R/W 0	R/W 0
E	Bit/Field		Nam	ne	Тур	е	Reset	Desc	cription							
	31:20		reserv	ved	R	O	0x000	com	patibility	ould not i with futu cross a re	ıre produ	ucts, the	value of	a reserv		
	19		INTFAL	JLT3	RΛ	N	0	Inter	rupt Fau	ılt 3						
								Valu	ie Desc	ription						
								0		ault cond to the int				3 is supp	oressed	and not
								1		terrupt is ition for F					nen the f	ault
	18		INTFAL	JLT2	R/\	N	0	Inter	rupt Fau	ılt 2						
								Valu	ie Desc	ription						
								0		ault cond to the int				2 is supp	ressed	and not
								1		terrupt is ition for F					nen the t	fault
	17		INTFAL	JLT1	R/\	N	0	Inter	rupt Fau	ılt 1						
									-							

Value Description

- The fault condition for PWM generator 1 is suppressed and not sent to the interrupt controller.
- 1 An interrupt is sent to the interrupt controller when the fault condition for PWM generator 1 is asserted.

Bit/Field	Name	Туре	Reset	Description
16	INTFAULT0	R/W	0	Interrupt Fault 0
				Value Description
				O The fault condition for PWM generator 0 is suppressed and not sent to the interrupt controller.
				An interrupt is sent to the interrupt controller when the fault condition for PWM generator 0 is asserted.
15:4	reserved	RO	0x000	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
3	INTPWM3	R/W	0	PWM3 Interrupt Enable
				Value Description
				The PWM generator 3 interrupt is suppressed and not sent to the interrupt controller.
				An interrupt is sent to the interrupt controller when the PWM generator 3 block asserts an interrupt.
2	INTPWM2	R/W	0	PWM2 Interrupt Enable
				Value Description
				O The PWM generator 2 interrupt is suppressed and not sent to the interrupt controller.
				An interrupt is sent to the interrupt controller when the PWM generator 2 block asserts an interrupt.
1	INTPWM1	R/W	0	PWM1 Interrupt Enable
				Value Description
				The PWM generator 1 interrupt is suppressed and not sent to the interrupt controller.
				An interrupt is sent to the interrupt controller when the PWM generator 1 block asserts an interrupt.
0	INTPWM0	R/W	0	PWM0 Interrupt Enable
				Value Description
				The PWM generator 0 interrupt is suppressed and not sent to the interrupt controller.
				An interrupt is sent to the interrupt controller when the PWM generator 0 block asserts an interrupt.

Register 7: PWM Raw Interrupt Status (PWMRIS), offset 0x018

This register provides the current set of interrupt sources that are asserted, regardless of whether they are enabled to cause an interrupt to be asserted to the interrupt controller. The fault interrupt is asserted based on the fault condition source that is specified by the **PWMnCTL**, **PWMnFLTSRC0** and **PWMnFLTSRC1** registers. The fault interrupt is latched on detection and must be cleared through the **PWM Interrupt Status and Clear (PWMISC)** register. The actual value of the MnFAULTn signals can be observed using the **PWMSTATUS** register.

The PWM generator interrupts simply reflect the status of the PWM generators and are cleared via the interrupt status register in the PWM generator blocks. If a bit is set, the event is active; if a bit is clear the event is not active.

PWM Raw Interrupt Status (PWMRIS)

PWM0 base: 0x4002.8000 PWM1 base: 0x4002.9000 Offset 0x018 Type RO, reset 0x0000.0000

	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16
		1	·			rese	rved	1			1		INTFAULT3	INTFAULT2	INTFAULT1	INTFAULT0
Туре	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO
Reset	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0
	15	14	13	12	11	10	9	8	7	6	5	4	3	2	1	0
		•	•			rese	rved	•			1		INTPWM3	INTPWM2	INTPWM1	INTPWM0
Туре	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO
Reset	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0

Bit/Field	Name	Type	Reset	Description
31:20	reserved	RO	0x000	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
19	INTFAULT3	RO	0	Interrupt Fault PWM 3
				Value Description O The fault condition for PWM generator 3 has not been asserted. The fault condition for PWM generator 3 is asserted. This bit is cleared by writing a 1 to the INTFAULT3 bit in the PWMISC register.
18	INTFAULT2	RO	0	Interrupt Fault PWM 2

Value Description

- 0 The fault condition for PWM generator 2 has not been asserted.
- The fault condition for PWM generator 2 is asserted.

This bit is cleared by writing a 1 to the ${\tt INTFAULT2}$ bit in the ${\tt PWMISC}$ register.

Bit/Field	Name	Туре	Reset	Description
17	INTFAULT1	RO	0	Interrupt Fault PWM 1
				Value Description
				0 The fault condition for PWM generator 1 has not been asserted.
				1 The fault condition for PWM generator 1 is asserted.
				This bit is cleared by writing a 1 to the ${\tt INTFAULT1}$ bit in the ${\tt PWMISC}$ register.
16	INTFAULT0	RO	0	Interrupt Fault PWM 0
				Value Description
				0 The fault condition for PWM generator 0 has not been asserted.
				1 The fault condition for PWM generator 0 is asserted.
				This bit is cleared by writing a 1 to the ${\tt INTFAULT0}$ bit in the ${\tt PWMISC}$ register.
15:4	reserved	RO	0x000	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
3	INTPWM3	RO	0	PWM3 Interrupt Asserted
				Value Description
				0 The PWM generator 3 block interrupt has not been asserted.
				1 The PWM generator 3 block interrupt is asserted.
				The PWM3RIS register shows the source of this interrupt. This bit is cleared by writing a 1 to the corresponding bit in the PWM3ISC register.
2	INTPWM2	RO	0	PWM2 Interrupt Asserted
				Value Description
				The PWM generator 2 block interrupt has not been asserted.
				1 The PWM generator 2 block interrupt is asserted.
				The PWM2RIS register shows the source of this interrupt. This bit is cleared by writing a 1 to the corresponding bit in the PWM2ISC register.
1	INTPWM1	RO	0	PWM1 Interrupt Asserted
				Value Description
				The PWM generator 1 block interrupt has not been asserted.
				1 The PWM generator 1 block interrupt is asserted.

The **PWM1RIS** register shows the source of this interrupt. This bit is cleared by writing a 1 to the corresponding bit in the **PWM1ISC** register.

Bit/Field	Name	Туре	Reset	Description
0	INTPWM0	RO	0	PWM0 Interrupt Asserted
				Value Description The PWM generator 0 block interrupt has not been asserted. The PWM generator 0 block interrupt is asserted.

The **PWM0RIS** register shows the source of this interrupt. This bit is cleared by writing a 1 to the corresponding bit in the **PWM0ISC** register.

Register 8: PWM Interrupt Status and Clear (PWMISC), offset 0x01C


This register provides a summary of the interrupt status of the individual PWM generator blocks. If a fault interrupt is set, the corresponding MnFAULTn input has caused an interrupt. For the fault interrupt, a write of 1 to that bit position clears the latched interrupt status. If an block interrupt bit is set, the corresponding generator block is asserting an interrupt. The individual interrupt status registers, **PWMnISC**, in each block must be consulted to determine the reason for the interrupt and used to clear the interrupt.

PWM Interrupt Status and Clear (PWMISC)

PWM0 base: 0x4002.8000 PWM1 base: 0x4002.9000

Offset 0x01C

Type R/W1C, reset 0x0000.0000



- The fault condition for PWM generator 3 has not been asserted or is not enabled.
- 1 An enabled interrupt for the fault condition for PWM generator 3 is asserted or is latched.

Writing a 1 to this bit clears it and the ${\tt INTFAULT3}$ bit in the PWMRIS register.

18 INTFAULT2 R/W1C 0 FAULT2 Interrupt Asserted

Value Description

- The fault condition for PWM generator 2 has not been asserted or is not enabled.
- An enabled interrupt for the fault condition for PWM generator 2 is asserted or is latched.

Writing a 1 to this bit clears it and the ${\tt INTFAULT2}$ bit in the PWMRIS register.

Bit/Field	Name	Туре	Reset	Description
17	INTFAULT1	R/W1C	0	FAULT1 Interrupt Asserted
				Value Description
				The fault condition for PWM generator 1 has not been asserted or is not enabled.
				An enabled interrupt for the fault condition for PWM generator 1 is asserted or is latched.
				Writing a 1 to this bit clears it and the INTFAULT1 bit in the PWMRIS register.
16	INTFAULT0	R/W1C	0	FAULT0 Interrupt Asserted
				Value Description
				The fault condition for PWM generator 0 has not been asserted or is not enabled.
				An enabled interrupt for the fault condition for PWM generator 0 is asserted or is latched.
				Writing a 1 to this bit clears it and the INTFAULT0 bit in the PWMRIS register.
15:4	reserved	RO	0x000	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
3	INTPWM3	RO	0	PWM3 Interrupt Status
				Value Description
				The PWM generator 3 block interrupt is not asserted or is not enabled.
				1 An enabled interrupt for the PWM generator 3 block is asserted.
				The PWM3RIS register shows the source of this interrupt. This bit is cleared by writing a 1 to the corresponding bit in the PWM3ISC register.
2	INTPWM2	RO	0	PWM2 Interrupt Status
				Value Description
				The PWM generator 2 block interrupt is not asserted or is not enabled.
				1 An enabled interrupt for the PWM generator 2 block is asserted.
				The PWM2RIS register shows the source of this interrupt. This bit is cleared by writing a 1 to the corresponding bit in the PWM2ISC register.
1	INTPWM1	RO	0	PWM1 Interrupt Status
				Value Description
				The PWM generator 1 block interrupt is not asserted or is not enabled.
				1 An enabled interrupt for the PWM generator 1 block is asserted.
				The PWM1RIS register shows the source of this interrupt. This bit is cleared by writing a 1 to the corresponding bit in the PWM1ISC register.

Bit/Field	Name	Туре	Reset	Description
0	INTPWM0	RO	0	PWM0 Interrupt Status
				Value Description
				The PWM generator 0 block interrupt is not asserted or is not enabled.
				1 An enabled interrupt for the PWM generator 0 block is asserted.

The **PWM0RIS** register shows the source of this interrupt. This bit is cleared by writing a 1 to the corresponding bit in the **PWM0ISC** register.

Register 9: PWM Status (PWMSTATUS), offset 0x020

This register provides the unlatched status of the PWM generator fault condition.

PWM Status (PWMSTATUS)

PWM0 base: 0x4002.8000 PWM1 base: 0x4002.9000 Offset 0x020

Type RO, reset 0x0000.0000

	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16
		1		1				rese	rved			1				
Type	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO
Reset	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0
	15	14	13	12	11	10	9	8	7	6	5	4	3	2	1	0
						reserved							FAULT3	FAULT2	FAULT1	FAULT0
Туре	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO
Reset	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0

															l	
Type eset	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0
В	sit/Field		Nam	e	Тур	ре	Reset	Des	cription							
	31:4		reserv	red	R)	0x0000.000	com	ware sho patibility served ac	with fut	ure produ	ucts, the	value of	a reserv	•	
	3		FAUL	Т3	R	O	0	Gen	erator 3	Fault St	atus					
								Valu	ue Desc	ription						
								0	The f	ault con	dition for	PWM g	enerator	3 is not	asserted	d.
								1	The f	ault con	dition for	PWM g	enerator	3 is ass	erted.	
												e PWM3 ult condi	•	•		•
	2		FAUL	T2	R	Э	0	Gen	erator 2	Fault St	atus					
								Valu	ue Desc	ription						
								0	The f	ault con	dition for	PWM g	enerator	2 is not	asserted	d.
								1	The f	ault con	dition for	PWM g	enerator	2 is ass	erted.	
										e PWM2 ult condi	•	•		•		
	1		FAUL	T1	R)	0	Gen	erator 1	Fault St	atus					

Value Description

- The fault condition for PWM generator 1 is not asserted.
- 1 The fault condition for PWM generator 1 is asserted.
 If the FLTSRC bit in the PWM1CTL register is clear, the input is the source of the fault condition, and is therefore asserted.

Bit/Field	Name	Type	Reset	Description
0	FAULT0	RO	0	Generator 0 Fault Status

Value Description

- 0 The fault condition for PWM generator 0 is not asserted.
- 1 The fault condition for PWM generator 0 is asserted.

 If the FLTSRC bit in the **PWM0CTL** register is clear, the input is the source of the fault condition, and is therefore asserted.

Register 10: PWM Fault Condition Value (PWMFAULTVAL), offset 0x024


This register specifies the output value driven on the MnPWMn signals during a fault condition if enabled by the corresponding bit in the **PWMFAULT** register. Note that if the corresponding bit in the **PWMINVERT** register is set, the output value is driven to the logical NOT of the bit value in this register.

PWM Fault Condition Value (PWMFAULTVAL)

PWM0 base: 0x4002.8000 PWM1 base: 0x4002.9000

Offset 0x024

Type R/W, reset 0x0000.0000



Bit/Field	Name	Type	Reset	Description
31:8	reserved	RO	0x0000.00	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
7	PWM7	R/W	0	MnPWM7 Fault Value
				Value Description
				The MnPWM7 output signal is driven Low during fault conditions if the FAULT7 bit in the PWMFAULT register is set.
				The MnPWM7 output signal is driven High during fault conditions if the FAULT7 bit in the PWMFAULT register is set.
6	PWM6	R/W	0	Mn₽WM6 Fault Value
				Value Description
				The MnPWM6 output signal is driven Low during fault conditions if the FAULT6 bit in the PWMFAULT register is set.
				1 The MnPWM6 output signal is driven High during fault conditions if the FAULT6 bit in the PWMFAULT register is set.
5	PWM5	R/W	0	MnPWM5 Fault Value
				Value Description

- 0 The MnPWM5 output signal is driven Low during fault conditions if the ${\tt FAULT5}$ bit in the ${\tt PWMFAULT}$ register is set.
- 1 The MnPWM5 output signal is driven High during fault conditions if the FAULT5 bit in the **PWMFAULT** register is set.

Bit/Field	Name	Туре	Reset	Description
4	PWM4	R/W	0	MnPWM4 Fault Value
				Value Description
				The MnPWM4 output signal is driven Low during fault conditions if the FAULT4 bit in the PWMFAULT register is set.
				The MnPWM4 output signal is driven High during fault conditions if the FAULT4 bit in the PWMFAULT register is set.
3	PWM3	R/W	0	MnPWM3 Fault Value
				Value Description
				The MnPWM3 output signal is driven Low during fault conditions if the FAULT3 bit in the PWMFAULT register is set.
				1 The MnPWM3 output signal is driven High during fault conditions if the FAULT3 bit in the PWMFAULT register is set.
2	PWM2	R/W	0	MnPWM2 Fault Value
				Value Description
				The MnPWM2 output signal is driven Low during fault conditions if the FAULT2 bit in the PWMFAULT register is set.
				1 The MnPWM2 output signal is driven High during fault conditions if the FAULT2 bit in the PWMFAULT register is set.
1	PWM1	R/W	0	MnPWM1 Fault Value
				Value Description
				The MnPWM1 output signal is driven Low during fault conditions if the FAULT1 bit in the PWMFAULT register is set.
				1 The MnPWM1 output signal is driven High during fault conditions if the FAULT1 bit in the PWMFAULT register is set.
0	PWM0	R/W	0	MnPWM0 Fault Value
				Value Description
				The MnPWM0 output signal is driven Low during fault conditions if the FAULT0 bit in the PWMFAULT register is set.
				1 The MnPWM0 output signal is driven High during fault conditions if the FAULT0 bit in the PWMFAULT register is set.

Register 11: PWM Enable Update (PWMENUPD), offset 0x028


This register specifies when updates to the PWMnEN bit in the **PWMENABLE** register are performed. The PWMnEN bit enables the pwmA' or pwmB' output to be passed to the microcontroller's pin. Updates can be immediate or locally or globally synchronized to the next synchronous update.

PWM Enable Update (PWMENUPD)

PWM0 base: 0x4002.8000 PWM1 base: 0x4002.9000

Offset 0x028

Type R/W, reset 0x0000.0000



Bit/Field	Name	Type	Reset	Description
31:16	reserved	RO	0x00	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
15:14	ENUPD7	R/W	0	MnPWM7 Enable Update Mode

Value Description

0x0 Immediate

Writes to the PWM7EN bit in the **PWMENABLE** register are used by the PWM generator immediately.

0x1 Reserved

0x2 Locally Synchronized

Writes to the PWM7EN bit in the **PWMENABLE** register are used by the PWM generator the next time the counter is 0.

0x3 Globally Synchronized

Writes to the PWM7EN bit in the **PWMENABLE** register are used by the PWM generator the next time the counter is 0 after a synchronous update has been requested through the PWM Master Control (**PWMCTL**) register.

Bit/Field	Name	Туре	Reset	Description
13:12	ENUPD6	R/W	0	MnPWM6 Enable Update Mode
				 Value Description 0x0 Immediate Writes to the PWM6EN bit in the PWMENABLE register are used by the PWM generator immediately. 0x1 Reserved 0x2 Locally Synchronized Writes to the PWM6EN bit in the PWMENABLE register are used by the PWM generator the next time the counter is 0. 0x3 Globally Synchronized Writes to the PWM6EN bit in the PWMENABLE register are used by the PWM generator the next time the counter is 0 after a synchronous update has been requested through the PWM Master Control (PWMCTL) register.
11:10	ENUPD5	R/W	0	 Value Description 0x0 Immediate Writes to the PWM5EN bit in the PWMENABLE register are used by the PWM generator immediately. 0x1 Reserved 0x2 Locally Synchronized Writes to the PWM5EN bit in the PWMENABLE register are used by the PWM generator the next time the counter is 0. 0x3 Globally Synchronized Writes to the PWM5EN bit in the PWMENABLE register are used by the PWM generator the next time the counter is 0 after a synchronous update has been requested through the PWM Master Control (PWMCTL) register.
9:8	ENUPD4	R/W	0	 Value Description 0x0 Immediate Writes to the PWM4EN bit in the PWMENABLE register are used by the PWM generator immediately. 0x1 Reserved 0x2 Locally Synchronized Writes to the PWM4EN bit in the PWMENABLE register are used by the PWM generator the next time the counter is 0. 0x3 Globally Synchronized Writes to the PWM4EN bit in the PWMENABLE register are used by the PWM generator the next time the counter is 0 after a synchronous update has been requested through the PWM Master Control (PWMCTL) register.

Bit/Field	Name	Туре	Reset	Description
7:6	ENUPD3	R/W	0	MnPWM3 Enable Update Mode
				Value Description
				0x0 Immediate
				Writes to the PWM3EN bit in the PWMENABLE register are used by the PWM generator immediately.
				0x1 Reserved
				0x2 Locally Synchronized
				Writes to the PWM3EN bit in the PWMENABLE register are used by the PWM generator the next time the counter is 0.
				0x3 Globally Synchronized
				Writes to the PWM3EN bit in the PWMENABLE register are used by the PWM generator the next time the counter is 0 after a synchronous update has been requested through the PWM Master Control (PWMCTL) register.
5:4	ENUPD2	R/W	0	MnPWM2 Enable Update Mode
				Value Description
				0x0 Immediate
				Writes to the PWM2EN bit in the PWMENABLE register are used by the PWM generator immediately.
				0x1 Reserved
				0x2 Locally Synchronized
				Writes to the PWM2EN bit in the PWMENABLE register are used by the PWM generator the next time the counter is 0.
				0x3 Globally Synchronized
				Writes to the PWM2EN bit in the PWMENABLE register are used by the PWM generator the next time the counter is 0 after a synchronous update has been requested through the PWM Master Control (PWMCTL) register.
3:2	ENUPD1	R/W	0	MnPWM1 Enable Update Mode
				Value Description
				0x0 Immediate
				Writes to the PWM1EN bit in the PWMENABLE register are used by the PWM generator immediately.
				0x1 Reserved
				0x2 Locally Synchronized
				Writes to the PWM1EN bit in the PWMENABLE register are used by the PWM generator the next time the counter is 0.
				0x3 Globally Synchronized
				Writes to the PWM1EN bit in the PWMENABLE register are used by the PWM generator the next time the counter is 0 after a synchronous update has been requested through the PWM Master Control (PWMCTL) register.

Bit/Field	Name	Туре	Reset	Description
1:0	ENUPD0	R/W	0	MnPWM0 Enable Update Mode
				Value Description
				0x0 Immediate
				Writes to the PWM0EN bit in the PWMENABLE register are used by the PWM generator immediately.
				0x1 Reserved
				0x2 Locally Synchronized
				Writes to the PWM0EN bit in the PWMENABLE register are used by the PWM generator the next time the counter is 0.
				0x3 Globally Synchronized
				Writes to the PWM0EN bit in the PWMENABLE register are used by the PWM generator the next time the counter is 0 after a synchronous update has been requested through the PWM Master Control (PWMCTL) register.

Register 12: PWM0 Control (PWM0CTL), offset 0x040

Register 13: PWM1 Control (PWM1CTL), offset 0x080

Register 14: PWM2 Control (PWM2CTL), offset 0x0C0

Register 15: PWM3 Control (PWM3CTL), offset 0x100


These registers configure the PWM signal generation blocks (PWM0CTL controls the PWM generator 0 block, and so on). The Register Update mode, Debug mode, Counting mode, and Block Enable mode are all controlled via these registers. The blocks produce the PWM signals, which can be either two independent PWM signals (from the same counter), or a paired set of PWM signals with dead-band delays added.

The PWM0 block produces the MnPWM0 and MnPWM1 outputs, the PWM1 block produces the MnPWM2 and MnPWM3 outputs, the PWM2 block produces the MnPWM4 and MnPWM5 outputs, and the PWM3 block produces the MnPWM6 and MnPWM7 outputs.

PWMn Control (PWMnCTL)

PWM0 base: 0x4002.8000 PWM1 base: 0x4002.9000

Offset 0x040 Type R/W, reset 0x0000.0000



Bit/Field	Name	Type	Reset	Description
31:19	reserved	RO	0x000	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
18	LATCH	R/W	0	Latch Fault Input

Value Description

Fault Condition Not Latched
 A fault condition is in effect for as long as the generating source is asserting.

1 Fault Condition Latched

A fault condition is set as the result of the assertion of the faulting source and is held (latched) while the **PWMISC** INTFAULTn bit is set. Clearing the INTFAULTn bit clears the fault condition.

Bit/Field	Name	Туре	Reset	Description
17	MINFLTPER	R/W	0	Minimum Fault Period
				This bit specifies that the PWM generator enables a one-shot counter to provide a minimum fault condition period.
				The timer begins counting on the rising edge of the fault condition to extend the condition for a minimum duration of the count value. The timer ignores the state of the fault condition while counting.
				The minimum fault delay is in effect only when the MINFLTPER bit is set. If a detected fault is in the process of being extended when the MINFLTPER bit is cleared, the fault condition extension is aborted.
				The delay time is specified by the PWMnMINFLTPER register MFP field value. The effect of this is to pulse stretch the fault condition input.
				The delay value is defined by the PWM clock period. Because the fault input is not synchronized to the PWM clock, the period of the time is PWMClock * (MFP value + 1) or PWMClock * (MFP value + 2).
				The delay function makes sense only if the fault source is unlatched. A latched fault source makes the fault condition appear asserted until cleared by software and negates the utility of the extend feature. It applies to all fault condition sources as specified in the FLTSRC field.
				Value Description
				0 The FAULT input deassertion is unaffected.
				The PWMnMINFLTPER one-shot counter is active and extends the period of the fault condition to a minimum period.
16	FLTSRC	R/W	0	Fault Condition Source
				Value Description
				O The Fault condition is determined by the Fault 0 input.
				The Fault condition is determined by the configuration of the PWMnFLTSRC0 and PWMnFLTSRC1 registers.
15:14	DBFALLUPD	R/W	0x0	PWMnDBFALL Update Mode
				Value Description
				0x0 Immediate
				The PWMnDBFALL register value is immediately updated on a write.
				0x1 Reserved
				0x2 Locally Synchronized
				Updates to the register are reflected to the generator the next time the counter is 0.
				0x3 Globally Synchronized
				Updates to the register are delayed until the next time the counter is 0 after a synchronous update has been requested through the PWMCTL register.

Bit/Field	Name	Туре	Reset	Description
13:12	DBRISEUPD	R/W	0x0	PWMnDBRISE Update Mode
				Value Description 0x0 Immediate The PWMnDBRISE register value is immediately updated on a write. 0x1 Reserved 0x2 Locally Synchronized Updates to the register are reflected to the generator the next time the counter is 0. 0x3 Globally Synchronized Updates to the register are delayed until the next time the
				counter is 0 after a synchronous update has been requested through the PWMCTL register.
11:10	DBCTLUPD	R/W	0x0	PWMnDBCTL Update Mode
				Value Description
				0x0 Immediate
				The PWMnDBCTL register value is immediately updated on a write.
				0x1 Reserved
				0x2 Locally Synchronized
				Updates to the register are reflected to the generator the next time the counter is 0.
				0x3 Globally Synchronized
				Updates to the register are delayed until the next time the counter is 0 after a synchronous update has been requested through the PWMCTL register.
9:8	GENBUPD	R/W	0x0	PWMnGENB Update Mode
				Value Description
				0x0 Immediate
				The PWMnGENB register value is immediately updated on a write.
				0x1 Reserved
				0x2 Locally Synchronized
				Updates to the register are reflected to the generator the next time the counter is 0.
				0x3 Globally Synchronized
				Updates to the register are delayed until the next time the counter is 0 after a synchronous update has been requested through the PWMCTL register.

Bit/Field	Name	Туре	Reset	Description
7:6	GENAUPD	R/W	0x0	PWMnGENA Update Mode
				Value Description
				0x0 Immediate
				The PWMnGENA register value is immediately updated on a write.
				0x1 Reserved
				0x2 Locally Synchronized
				Updates to the register are reflected to the generator the next time the counter is 0.
				0x3 Globally Synchronized
				Updates to the register are delayed until the next time the counter is 0 after a synchronous update has been requested through the PWMCTL register.
5	CMPBUPD	R/W	0	Comparator B Update Mode
				Value Description
				0 Locally Synchronized
				Updates to the PWMnCMPB register are reflected to the generator the next time the counter is 0.
				1 Globally Synchronized
				Updates to the register are delayed until the next time the counter is 0 after a synchronous update has been requested through the PWMCTL register.
4	CMPAUPD	R/W	0	Comparator A Update Mode
				Value Description
				0 Locally Synchronized
				Updates to the PWMnCMPA register are reflected to the generator the next time the counter is 0.
				1 Globally Synchronized
				Updates to the register are delayed until the next time the counter is 0 after a synchronous update has been requested through the PWMCTL register.
3	LOADUPD	R/W	0	Load Register Update Mode
				Value Description
				0 Locally Synchronized
				Updates to the PWMnLOAD register are reflected to the generator the next time the counter is 0.
				1 Globally Synchronized
				Updates to the register are delayed until the next time the counter is 0 after a synchronous update has been requested through the PWMCTL register.

Bit/Field	Name	Туре	Reset	Description
2	DEBUG	R/W	0	Debug Mode
				Value Description
				0 The counter stops running when it next reaches 0 and continues running again when no longer in Debug mode.
				1 The counter always runs when in Debug mode.
1	MODE	R/W	0	Counter Mode
				Value Description
				The counter counts down from the load value to 0 and then wraps back to the load value (Count-Down mode).
				1 The counter counts up from 0 to the load value, back down to 0, and then repeats (Count-Up/Down mode).
0	ENABLE	R/W	0	PWM Block Enable
				Value Description
				0 The entire PWM generation block is disabled and not clocked.

- The entire PWM generation block is disabled and not clocked.
- 1 The PWM generation block is enabled and produces PWM signals.

Register 16: PWM0 Interrupt and Trigger Enable (PWM0INTEN), offset 0x044 Register 17: PWM1 Interrupt and Trigger Enable (PWM1INTEN), offset 0x084 Register 18: PWM2 Interrupt and Trigger Enable (PWM2INTEN), offset 0x0C4 Register 19: PWM3 Interrupt and Trigger Enable (PWM3INTEN), offset 0x104

These registers control the interrupt and ADC trigger generation capabilities of the PWM generators (**PWM0INTEN** controls the PWM generator 0 block, and so on). The events that can cause an interrupt,or an ADC trigger are:

- The counter being equal to the load register
- The counter being equal to zero
- The counter being equal to the **PWMnCMPA** register while counting up
- The counter being equal to the **PWMnCMPA** register while counting down
- The counter being equal to the **PWMnCMPB** register while counting up
- The counter being equal to the **PWMnCMPB** register while counting down


Any combination of these events can generate either an interrupt or an ADC trigger, though no determination can be made as to the actual event that caused an ADC trigger if more than one is specified. The **PWMnRIS** register provides information about which events have caused raw interrupts.

PWMn Interrupt and Trigger Enable (PWMnINTEN)

PWM0 base: 0x4002.8000 PWM1 base: 0x4002.9000

Offset 0x044

Type R/W, reset 0x0000.0000



Bit/Field	Name	Type	Reset	Description
31:14	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
13	TRCMPBD	R/W	0	Trigger for Counter=PWMnCMPB Down

Value Description

- 0 No ADC trigger is output.
- An ADC trigger pulse is output when the counter matches the value in the **PWMnCMPB** register value while counting down.

Bit/Field	Name	Туре	Reset	Description
12	TRCMPBU	R/W	0	Trigger for Counter= PWMnCMPB Up
				Value Description
				0 No ADC trigger is output.
				An ADC trigger pulse is output when the counter matches the value in the PWMnCMPB register value while counting up.
11	TRCMPAD	R/W	0	Trigger for Counter= PWMnCMPA Down
				Value Description
				0 No ADC trigger is output.
				An ADC trigger pulse is output when the counter matches the value in the PWMnCMPA register value while counting down.
10	TRCMPAU	R/W	0	Trigger for Counter= PWMnCMPA Up
				Value Description
				0 No ADC trigger is output.
				1 An ADC trigger pulse is output when the counter matches the value in the PWMnCMPA register value while counting up.
9	TRCNTLOAD	R/W	0	Trigger for Counter= PWMnLOAD
				Value Description
				0 No ADC trigger is output.
				An ADC trigger pulse is output when the counter matches the PWMnLOAD register.
8	TRCNTZERO	R/W	0	Trigger for Counter=0
				Value Description
				0 No ADC trigger is output.
				1 An ADC trigger pulse is output when the counter is 0.
7:6	reserved	RO	0x0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
5	INTCMPBD	R/W	0	Interrupt for Counter=PWMnCMPB Down
				Value Description
				0 No interrupt.
				A raw interrupt occurs when the counter matches the value in the PWMnCMPB register value while counting down.

Bit/Field	Name	Туре	Reset	Description
4	INTCMPBU	R/W	0	Interrupt for Counter=PWMnCMPB Up
				Value Description
				0 No interrupt.
				A raw interrupt occurs when the counter matches the value in the PWMnCMPB register value while counting up.
3	INTCMPAD	R/W	0	Interrupt for Counter= PWMnCMPA Down
				Value Description
				0 No interrupt.
				A raw interrupt occurs when the counter matches the value in the PWMnCMPA register value while counting down.
2	INTCMPAU	R/W	0	Interrupt for Counter= PWMnCMPA Up
				Value Description
				0 No interrupt.
				A raw interrupt occurs when the counter matches the value in the PWMnCMPA register value while counting up.
1	INTCNTLOAD	R/W	0	Interrupt for Counter=PWMnLOAD
				Value Description
				0 No interrupt.
				A raw interrupt occurs when the counter matches the value in the PWMnLOAD register value.
0	INTCNTZERO	R/W	0	Interrupt for Counter=0
				Value Description
				0 No interrupt.
				1 A raw interrupt occurs when the counter is zero.

Register 20: PWM0 Raw Interrupt Status (PWM0RIS), offset 0x048

Register 21: PWM1 Raw Interrupt Status (PWM1RIS), offset 0x088

Register 22: PWM2 Raw Interrupt Status (PWM2RIS), offset 0x0C8

Register 23: PWM3 Raw Interrupt Status (PWM3RIS), offset 0x108


These registers provide the current set of interrupt sources that are asserted, regardless of whether they cause an interrupt to be asserted to the controller (**PWM0RIS** controls the PWM generator 0 block, and so on). If a bit is set, the event has occurred; if a bit is clear, the event has not occurred. Bits in this register are cleared by writing a 1 to the corresponding bit in the **PWMnISC** register.

PWMn Raw Interrupt Status (PWMnRIS)

PWM0 base: 0x4002.8000 PWM1 base: 0x4002.9000

Offset 0x048

Type RO, reset 0x0000.0000



Bit/Field	Name	Туре	Reset	Description
31:6	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
5	INTCMPBD	RO	0	Comparator B Down Interrupt Status
				Value Description
				0 An interrupt has not occurred.
				1 The counter has matched the value in the PWMnCMPB register while counting down.
				This bit is cleared by writing a 1 to the ${\tt INTCMPBD}$ bit in the $\textbf{PWMnISC}$ register.
4	INTCMPBU	RO	0	Comparator B Up Interrupt Status

Value Description

- 0 An interrupt has not occurred.
- The counter has matched the value in the **PWMnCMPB** register while counting up.

This bit is cleared by writing a 1 to the ${\tt INTCMPBU}$ bit in the ${\tt PWMnISC}$ register.

Bit/Field	Name	Туре	Reset	Description
3	INTCMPAD	RO	0	Comparator A Down Interrupt Status
				Value Description
				0 An interrupt has not occurred.
				1 The counter has matched the value in the PWMnCMPA register while counting down.
				This bit is cleared by writing a 1 to the ${\tt INTCMPAD}$ bit in the ${\tt PWMnISC}$ register.
2	INTCMPAU	RO	0	Comparator A Up Interrupt Status
				Value Description
				0 An interrupt has not occurred.
				1 The counter has matched the value in the PWMnCMPA register while counting up.
				This bit is cleared by writing a 1 to the INTCMPAU bit in the PWMnISC register.
1	INTCNTLOAD	RO	0	Counter=Load Interrupt Status
				Value Description
				0 An interrupt has not occurred.
				1 The counter has matched the value in the PWMnLOAD register.
				This bit is cleared by writing a 1 to the INTCNTLOAD bit in the PWMnISC register.
0	INTCNTZERO	RO	0	Counter=0 Interrupt Status
				Value Description
				0 An interrupt has not occurred.
				1 The counter has matched zero.
				This bit is cleared by writing a 1 to the ${\tt INTCNTZERO}$ bit in the ${\tt PWMnISC}$ register.

Register 24: PWM0 Interrupt Status and Clear (PWM0ISC), offset 0x04C Register 25: PWM1 Interrupt Status and Clear (PWM1ISC), offset 0x08C Register 26: PWM2 Interrupt Status and Clear (PWM2ISC), offset 0x0CC Register 27: PWM3 Interrupt Status and Clear (PWM3ISC), offset 0x10C


These registers provide the current set of interrupt sources that are asserted to the interrupt controller (**PWM0ISC** controls the PWM generator 0 block, and so on). A bit is set if the event has occurred and is enabled in the **PWMnINTEN** register; if a bit is clear, the event has not occurred or is not enabled. These are R/W1C registers; writing a 1 to a bit position clears the corresponding interrupt reason.

PWMn Interrupt Status and Clear (PWMnISC)

PWM0 base: 0x4002.8000 PWM1 base: 0x4002.9000

Offset 0x04C

Type R/W1C, reset 0x0000.0000



Bit/Field	Name	Type	Reset	Description
31:6	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
5	INTCMPBD	R/W1C	0	Comparator B Down Interrupt
				Value Description
				0 No interrupt has occurred or the interrupt is masked.
				1 The INTCMPBD bits in the PWMnRIS and PWMnINTEN registers are set, providing an interrupt to the interrupt controller.
				This bit is cleared by writing a 1. Clearing this bit also clears the INTCMPBD bit in the PWMnRIS register.
4	INTCMPBU	R/W1C	0	Comparator B Up Interrupt

Value Description

- 0 No interrupt has occurred or the interrupt is masked.
- 1 The INTCMPBU bits in the **PWMnRIS** and **PWMnINTEN** registers are set, providing an interrupt to the interrupt controller.

This bit is cleared by writing a 1. Clearing this bit also clears the INTCMPBU bit in the **PWMnRIS** register.

Bit/Field	Name	Туре	Reset	Description
3	INTCMPAD	R/W1C	0	Comparator A Down Interrupt
				Value Description
				0 No interrupt has occurred or the interrupt is masked.
				1 The INTCMPAD bits in the PWMnRIS and PWMnINTEN registers are set, providing an interrupt to the interrupt controller.
				This bit is cleared by writing a 1. Clearing this bit also clears the INTCMPAD bit in the PWMnRIS register.
2	INTCMPAU	R/W1C	0	Comparator A Up Interrupt
				Value Description
				0 No interrupt has occurred or the interrupt is masked.
				1 The INTCMPAU bits in the PWMnRIS and PWMnINTEN registers are set, providing an interrupt to the interrupt controller.
				This bit is cleared by writing a 1. Clearing this bit also clears the INTCMPAU bit in the PWMnRIS register.
1	INTCNTLOAD	R/W1C	0	Counter=Load Interrupt
				Value Description
				0 No interrupt has occurred or the interrupt is masked.
				1 The INTCNTLOAD bits in the PWMnRIS and PWMnINTEN registers are set, providing an interrupt to the interrupt controller.
				This bit is cleared by writing a 1. Clearing this bit also clears the INTCNTLOAD bit in the PWMnRIS register.
0	INTCNTZERO	R/W1C	0	Counter=0 Interrupt
				Value Description
				No interrupt has occurred or the interrupt is masked.
				1 The INTENTZERO bits in the PWMnRIS and PWMnINTEN registers are set, providing an interrupt to the interrupt controller.
				This bit is cleared by writing a 1. Clearing this bit also clears the INTCNTZERO bit in the PWMnRIS register.

Register 28: PWM0 Load (PWM0LOAD), offset 0x050

Register 29: PWM1 Load (PWM1LOAD), offset 0x090

Register 30: PWM2 Load (PWM2LOAD), offset 0x0D0

Register 31: PWM3 Load (PWM3LOAD), offset 0x110

These registers contain the load value for the PWM counter (**PWM0LOAD** controls the PWM generator 0 block, and so on). Based on the counter mode configured by the MODE bit in the **PWMnCTL** register, this value is either loaded into the counter after it reaches zero or is the limit of up-counting after which the counter decrements back to zero. When this value matches the counter, a pulse is output which can be configured to drive the generation of the pwmA and/or pwmB signal (via the **PWMnGENA/PWMnGENB** register) or drive an interruptor ADC trigger (via the **PWMnINTEN** register).

If the Load Value Update mode is locally synchronized (based on the LOADUPD field encoding in the **PWMnCTL** register), the 16-bit LOAD value is used the next time the counter reaches zero. If the update mode is globally synchronized, it is used the next time the counter reaches zero after a synchronous update has been requested through the **PWM Master Control (PWMCTL)** register (see page 1249). If this register is re-written before the actual update occurs, the previous value is never used and is lost.

PWMn Load (PWMnLOAD)

PWM0 base: 0x4002.8000 PWM1 base: 0x4002.9000

Offset 0x050


15:0

LOAD

R/W

0x0000

Type R/W, reset 0x0000.0000



Counter Load Value
The counter load value.

Register 32: PWM0 Counter (PWM0COUNT), offset 0x054

Register 33: PWM1 Counter (PWM1COUNT), offset 0x094

Register 34: PWM2 Counter (PWM2COUNT), offset 0x0D4

Register 35: PWM3 Counter (PWM3COUNT), offset 0x114

These registers contain the current value of the PWM counter (**PWM0COUNT** is the value of the PWM generator 0 block, and so on). When this value matches zero or the value in the **PWMnLOAD**, **PWMnCMPA**, or **PWMnCMPB** registers, a pulse is output which can be configured to drive the generation of a PWM signal or drive an interrupt or ADC trigger.

PWMn Counter (PWMnCOUNT)

Namo

Type


Docot

PWM0 base: 0x4002.8000 PWM1 base: 0x4002.9000

Offset 0x054

Dit/Eiold

Type RO, reset 0x0000.0000



Divrieiu	Name	Type	Reset	Description
31:16	reserved	RO	0x0000	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
15:0	COUNT	RO	0x0000	Counter Value

Description

The current value of the counter.

Register 36: PWM0 Compare A (PWM0CMPA), offset 0x058

Register 37: PWM1 Compare A (PWM1CMPA), offset 0x098

Register 38: PWM2 Compare A (PWM2CMPA), offset 0x0D8

Register 39: PWM3 Compare A (PWM3CMPA), offset 0x118

These registers contain a value to be compared against the counter (**PWM0CMPA** controls the PWM generator 0 block, and so on). When this value matches the counter, a pulse is output which can be configured to drive the generation of the pwmA and pwmB signals (via the **PWMnGENA** and **PWMnGENB** registers) or drive an interrupt or ADC trigger (via the **PWMnINTEN** register). If the value of this register is greater than the **PWMnLOAD** register (see page 1286), then no pulse is ever output.


If the comparator A update mode is locally synchronized (based on the CMPAUPD bit in the **PWMnCTL** register), the 16-bit COMPA value is used the next time the counter reaches zero. If the update mode is globally synchronized, it is used the next time the counter reaches zero after a synchronous update has been requested through the **PWM Master Control (PWMCTL)** register (see page 1249). If this register is rewritten before the actual update occurs, the previous value is never used and is lost.

PWMn Compare A (PWMnCMPA)

PWM0 base: 0x4002.8000 PWM1 base: 0x4002.9000

Offset 0x058

Type R/W, reset 0x0000.0000



Register 40: PWM0 Compare B (PWM0CMPB), offset 0x05C

Register 41: PWM1 Compare B (PWM1CMPB), offset 0x09C

Register 42: PWM2 Compare B (PWM2CMPB), offset 0x0DC


Register 43: PWM3 Compare B (PWM3CMPB), offset 0x11C

These registers contain a value to be compared against the counter (**PWM0CMPB** controls the PWM generator 0 block, and so on). When this value matches the counter, a pulse is output which can be configured to drive the generation of the pwmA and pwmB signals (via the **PWMnGENA** and **PWMnGENB** registers) or drive an interrupt or ADC trigger (via the **PWMnINTEN** register). If the value of this register is greater than the **PWMnLOAD** register, no pulse is ever output.

If the comparator B update mode is locally synchronized (based on the CMPBUPD bit in the **PWMnCTL** register), the 16-bit COMPB value is used the next time the counter reaches zero. If the update mode is globally synchronized, it is used the next time the counter reaches zero after a synchronous update has been requested through the **PWM Master Control (PWMCTL)** register (see page 1249). If this register is rewritten before the actual update occurs, the previous value is never used and is lost.

PWMn Compare B (PWMnCMPB)

PWM0 base: 0x4002.8000 PWM1 base: 0x4002.9000 Offset 0x05C Type R/W, reset 0x0000.0000



Bit/Field	Name	Туре	Reset	Description
31:16	reserved	RO	0x0000	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
15:0	СОМРВ	R/W	0x0000	Comparator B Value The value to be compared against the counter.

Register 44: PWM0 Generator A Control (PWM0GENA), offset 0x060

Register 45: PWM1 Generator A Control (PWM1GENA), offset 0x0A0

Register 46: PWM2 Generator A Control (PWM2GENA), offset 0x0E0

Register 47: PWM3 Generator A Control (PWM3GENA), offset 0x120

These registers control the generation of the pwmA signal based on the load and zero output pulses from the counter, as well as the compare A and compare B pulses from the comparators (**PWM0GENA** controls the PWM generator 0 block, and so on). When the counter is running in Count-Down mode, only four of these events occur; when running in Count-Up/Down mode, all six occur. These events provide great flexibility in the positioning and duty cycle of the resulting PWM signal.

The **PWM0GENA** register controls generation of the pwm0A signal; **PWM1GENA**, the pwm1A signal; **PWM2GENA**, the pwm2A signal; and **PWM3GENA**, the pwm3A signal.


If a zero or load event coincides with a compare A or compare B event, the zero or load action is taken and the compare A or compare B action is ignored. If a compare A event coincides with a compare B event, the compare A action is taken and the compare B action is ignored.

If the Generator A update mode is immediate (based on the GENAUPD field encoding in the **PWMnCTL** register), the ACTCMPBD, ACTCMPBU, ACTCMPAD, ACTCMPAU, ACTLOAD, and ACTZERO values are used immediately. If the update mode is locally synchronized, these values are used the next time the counter reaches zero. If the update mode is globally synchronized, these values are used the next time the counter reaches zero after a synchronous update has been requested through the **PWM Master Control (PWMCTL)** register (see page 1249). If this register is rewritten before the actual update occurs, the previous value is never used and is lost.

PWMn Generator A Control (PWMnGENA)

PWM0 base: 0x4002.8000 PWM1 base: 0x4002.9000 Offset 0x060

Type R/W, reset 0x0000.0000



preserved across a read-modify-write operation.

Bit/Field	Name	Туре	Reset	Description
11:10	ACTCMPBD	R/W	0x0	Action for Comparator B Down This field specifies the action to be taken when the counter matches comparator B while counting down.
				Value Description
				0x0 Do nothing.
				0x1 Invert pwmA.
				0x2 Drive pwmA Low.
				0x3 Drive pwmA High.
9:8	ACTCMPBU	R/W	0x0	Action for Comparator B Up
				This field specifies the action to be taken when the counter matches comparator B while counting up. This action can only occur when the MODE bit in the PWMnCTL register is set.
				Value Description
				0x0 Do nothing.
				0x1 Invert pwmA.
				0x2 Drive pwmA Low.
				0x3 Drive pwmA High.
7:6	ACTCMPAD	R/W	0x0	Action for Comparator A Down
				This field specifies the action to be taken when the counter matches comparator A while counting down.
				Value Description
				0x0 Do nothing.
				0x1 Invert pwmA.
				0x2 Drive pwmA Low.
				0x3 Drive pwmA High.
5:4	ACTCMPAU	R/W	0x0	Action for Comparator A Up This field specifies the action to be taken when the counter matches comparator A while counting up. This action can only occur when the MODE bit in the PWMnCTL register is set.
				Value Description
				0x0 Do nothing.
				0x1 Invert pwmA.
				0x2 Drive pwmA Low.
				0x3 Drive pwmA High.

Bit/Field	Name	Туре	Reset	Description
3:2	ACTLOAD	R/W	0x0	Action for Counter=LOAD
				This field specifies the action to be taken when the counter matches the value in the PWMnLOAD register.
				Value Description
				0x0 Do nothing.
				0x1 Invert pwmA.
				0x2 Drive pwmA Low.
				0x3 Drive pwmA High.
1:0	ACTZERO	R/W	0x0	Action for Counter=0
				This field specifies the action to be taken when the counter is zero.
				Value Description
				0x0 Do nothing.
				0x1 Invert pwmA.
				0x2 Drive pwmA Low.
				0x3 Drive pwmA High.

Register 48: PWM0 Generator B Control (PWM0GENB), offset 0x064 Register 49: PWM1 Generator B Control (PWM1GENB), offset 0x0A4 Register 50: PWM2 Generator B Control (PWM2GENB), offset 0x0E4 Register 51: PWM3 Generator B Control (PWM3GENB), offset 0x124

These registers control the generation of the pwmB signal based on the load and zero output pulses from the counter, as well as the compare A and compare B pulses from the comparators (**PWM0GENB** controls the PWM generator 0 block, and so on). When the counter is running in Count-Down mode, only four of these events occur; when running in Count-Up/Down mode, all six occur. These events provide great flexibility in the positioning and duty cycle of the resulting PWM signal.

The **PWM0GENB** register controls generation of the pwm0B signal; **PWM1GENB**, the pwm1B signal; **PWM2GENB**, the pwm2B signal; and **PWM3GENB**, the pwm3B signal.


If a zero or load event coincides with a compare A or compare B event, the zero or load action is taken and the compare A or compare B action is ignored. If a compare A event coincides with a compare B event, the compare B action is taken and the compare A action is ignored.

If the Generator B update mode is immediate (based on the GENBUPD field encoding in the **PWMnCTL** register), the ACTCMPBD, ACTCMPBU, ACTCMPAD, ACTCMPAU, ACTLOAD, and ACTZERO values are used immediately. If the update mode is locally synchronized, these values are used the next time the counter reaches zero. If the update mode is globally synchronized, these values are used the next time the counter reaches zero after a synchronous update has been requested through the **PWM Master Control (PWMCTL)** register (see page 1249). If this register is rewritten before the actual update occurs, the previous value is never used and is lost.

PWMn Generator B Control (PWMnGENB), offset 0x064

PWM0 base: 0x4002.8000 PWM1 base: 0x4002.9000 Offset 0x064

Type R/W, reset 0x0000.0000



preserved across a read-modify-write operation.

Bit/Field	Name	Туре	Reset	Description
11:10	ACTCMPBD	R/W	0x0	Action for Comparator B Down
				This field specifies the action to be taken when the counter matches comparator B while counting down.
				Value Description
				0x0 Do nothing.
				0x1 Invert pwmB.
				0x2 Drive pwmB Low.
				0x3 Drive pwmB High.
9:8	ACTCMPBU	R/W	0x0	Action for Comparator B Up
				This field specifies the action to be taken when the counter matches comparator B while counting up. This action can only occur when the MODE bit in the PWMnCTL register is set.
				Value Description
				0x0 Do nothing.
				0x1 Invert pwmB.
				0x2 Drive pwmB Low.
				0x3 Drive pwmB High.
7:6	ACTCMPAD	R/W	0x0	Action for Comparator A Down
				This field specifies the action to be taken when the counter matches comparator A while counting down.
				Value Description
				0x0 Do nothing.
				0x1 Invert pwmB.
				0x2 Drive pwmB Low.
				0x3 Drive pwmB High.
5:4	ACTCMPAU	R/W	0x0	Action for Comparator A Up
				This field specifies the action to be taken when the counter matches comparator A while counting up. This action can only occur when the MODE bit in the PWMnCTL register is set.
				Value Description
				0x0 Do nothing.
				0x1 Invert pwmB.
				0x2 Drive pwmB Low.
				0x3 Drive pwmB High.

Bit/Field	Name	Туре	Reset	Description
3:2	ACTLOAD	R/W	0x0	Action for Counter=LOAD This field specifies the action to be taken when the counter matches the load value.
				Value Description
				0x0 Do nothing.
				0x1 Invert pwmB.
				0x2 Drive pwmB Low.
				0x3 Drive pwmB High.
1:0	ACTZERO	R/W	0x0	Action for Counter=0
				This field specifies the action to be taken when the counter is 0.
				Value Description
				0x0 Do nothing.
				0x1 Invert pwmB.
				0x2 Drive pwmB Low.
				0x3 Drive pwmB High.

Register 52: PWM0 Dead-Band Control (PWM0DBCTL), offset 0x068

Register 53: PWM1 Dead-Band Control (PWM1DBCTL), offset 0x0A8

Register 54: PWM2 Dead-Band Control (PWM2DBCTL), offset 0x0E8

Register 55: PWM3 Dead-Band Control (PWM3DBCTL), offset 0x128


The **PWMnDBCTL** register controls the dead-band generator, which produces the MnPWMn signals based on the pwmA and pwmB signals. When disabled, the pwmA signal passes through to the pwmA' signal and the pwmB signal passes through to the pwmB' signal. When dead-band control is enabled, the pwmB signal is ignored, the pwmA' signal is generated by delaying the rising edge(s) of the pwmA signal by the value in the **PWMnDBRISE** register (see page 1297), and the pwmB' signal is generated by inverting the pwmA signal and delaying the falling edge(s) of the pwmA signal by the value in the **PWMnDBFALL** register (see page 1298). The Output Control block outputs the pwm0A' signal on the MnPWM0 signal and the pwm0B' signal on the MnPWM1 signal. In a similar manner, MnPWM2 and MnPWM3 are produced from the pwm1A' and pwm1B' signals, MnPWM4 and MnPWM5 are produced from the pwm2A' and pwm2B' signals, and MnPWM6 and MnPWM7 are produced from the pwm3A' and pwm3B' signals.

If the Dead-Band Control mode is immediate (based on the DBCTLUPD field encoding in the **PWMnCTL** register), the ENABLE bit value is used immediately. If the update mode is locally synchronized, this value is used the next time the counter reaches zero. If the update mode is globally synchronized, this value is used the next time the counter reaches zero after a synchronous update has been requested through the **PWM Master Control (PWMCTL)** register (see page 1249). If this register is rewritten before the actual update occurs, the previous value is never used and is lost.

PWMn Dead-Band Control (PWMnDBCTL)

PWM0 base: 0x4002.8000 PWM1 base: 0x4002.9000 Offset 0x068

Type R/W, reset 0x0000.0000



Bit/Field	Name	Type	Reset	Description
31:1	reserved	RO	0x0000.000	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
0	ENABLE	R/W	0	Dead-Band Generator Enable

Value Description

- The pwmA and pwmB signals pass through to the pwmA' and pwmB' signals unmodified.
- 1 The dead-band generator modifies the pwmA signal by inserting dead bands into the pwmA' and pwmB' signals.

Register 56: PWM0 Dead-Band Rising-Edge Delay (PWM0DBRISE), offset 0x06C

Register 57: PWM1 Dead-Band Rising-Edge Delay (PWM1DBRISE), offset 0x0AC

Register 58: PWM2 Dead-Band Rising-Edge Delay (PWM2DBRISE), offset 0x0FC

Register 59: PWM3 Dead-Band Rising-Edge Delay (PWM3DBRISE), offset 0x12C


The **PWMnDBRISE** register contains the number of clock cycles to delay the rising edge of the pwmA signal when generating the pwmA' signal. If the dead-band generator is disabled through the **PWMnDBCTL** register, this register is ignored. If the value of this register is larger than the width of a High pulse on the pwmA signal, the rising-edge delay consumes the entire High time of the signal, resulting in no High time on the output. Care must be taken to ensure that the pwmA High time always exceeds the rising-edge delay.

If the Dead-Band Rising-Edge Delay mode is immediate (based on the DBRISEUPD field encoding in the **PWMnCTL** register), the 12-bit RISEDELAY value is used immediately. If the update mode is locally synchronized, this value is used the next time the counter reaches zero. If the update mode is globally synchronized, this value is used the next time the counter reaches zero after a synchronous update has been requested through the **PWM Master Control (PWMCTL)** register (see page 1249). If this register is rewritten before the actual update occurs, the previous value is never used and is lost.

PWMn Dead-Band Rising-Edge Delay (PWMnDBRISE)

PWM0 base: 0x4002.8000 PWM1 base: 0x4002.9000 Offset 0x06C

Type R/W, reset 0x0000.0000



Bit/Field	Name	Type	Reset	Description
31:12	reserved	RO	0x0000.0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
11:0	RISEDELAY	R/W	0x000	Dead-Band Rise Delay

The number of clock cycles to delay the rising edge of pwmA' after the rising edge of pwmA.

Register 60: PWM0 Dead-Band Falling-Edge-Delay (PWM0DBFALL), offset 0x070

Register 61: PWM1 Dead-Band Falling-Edge-Delay (PWM1DBFALL), offset 0x0B0

Register 62: PWM2 Dead-Band Falling-Edge-Delay (PWM2DBFALL), offset 0x0F0

Register 63: PWM3 Dead-Band Falling-Edge-Delay (PWM3DBFALL), offset 0x130


The **PWMnDBFALL** register contains the number of clock cycles to delay the rising edge of the pwmB' signal from the falling edge of the pwmA signal. If the dead-band generator is disabled through the **PWMnDBCTL** register, this register is ignored. If the value of this register is larger than the width of a Low pulse on the pwmA signal, the falling-edge delay consumes the entire Low time of the signal, resulting in no Low time on the output. Care must be taken to ensure that the pwmA Low time always exceeds the falling-edge delay.

If the Dead-Band Falling-Edge-Delay mode is immediate (based on the DBFALLUP field encoding in the **PWMnCTL** register), the 12-bit FALLDELAY value is used immediately. If the update mode is locally synchronized, this value is used the next time the counter reaches zero. If the update mode is globally synchronized, this value is used the next time the counter reaches zero after a synchronous update has been requested through the **PWM Master Control (PWMCTL)** register (see page 1249). If this register is rewritten before the actual update occurs, the previous value is never used and is lost.

PWMn Dead-Band Falling-Edge-Delay (PWMnDBFALL)

PWM0 base: 0x4002.8000 PWM1 base: 0x4002.9000 Offset 0x070

Type R/W, reset 0x0000.0000



The number of clock cycles to delay the falling edge of pwmB' from the rising edge of pwmA.

Register 64: PWM0 Fault Source 0 (PWM0FLTSRC0), offset 0x074

Register 65: PWM1 Fault Source 0 (PWM1FLTSRC0), offset 0x0B4

Register 66: PWM2 Fault Source 0 (PWM2FLTSRC0), offset 0x0F4

Register 67: PWM3 Fault Source 0 (PWM3FLTSRC0), offset 0x134


This register specifies which fault pin inputs are used to generate a fault condition. Each bit in the following register indicates whether the corresponding fault pin is included in the fault condition. All enabled fault pins are ORed together to form the **PWMnFLTSRC0** portion of the fault condition. The **PWMnFLTSRC0** fault condition is then ORed with the **PWMnFLTSRC1** fault condition to generate the final fault condition for the PWM generator.

If the FLTSRC bit in the **PWMnCTL** register (see page 1274) is clear, only the Fault0 signal affects the fault condition generated. Otherwise, sources defined in **PWMnFLTSRC0** and **PWMnFLTSRC1** affect the fault condition generated.

PWMn Fault Source 0 (PWMnFLTSRC0)

PWM0 base: 0x4002.8000 PWM1 base: 0x4002.9000

Offset 0x074 Type R/W, reset 0x0000.0000



Bit/Field	Name	Type	Reset	Description
31:4	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
3	FAULT3	R/W	0	Fault3 Input

Value Description

- The Fault3 signal is suppressed and cannot generate a fault condition
- 1 The Fault3 signal value is ORed with all other fault condition generation inputs (Faultn signals and digital comparators).

Note: The FLTSRC bit in the **PWMnCTL** register must be set for this bit to affect fault condition generation.

Bit/Field	Name	Туре	Reset	Description			
2	FAULT2	R/W	0	Fault2 Input			
				Value Description			
				0 The Fault2 signal is suppressed and cannot generate a fau condition.	ılt		
				1 The Fault2 signal value is ORed with all other fault condition generation inputs (Faultn signals and digital comparators).			
				Note: The FLTSRC bit in the PWMnCTL register must be set for the bit to affect fault condition generation.	nis		
1	FAULT1	R/W	0	Fault1 Input			
				Value Description			
				0 The Fault1 signal is suppressed and cannot generate a fau condition.	ılt		
				1 The Fault1 signal value is ORed with all other fault condition generation inputs (Faultn signals and digital comparators).			
				Note: The FLTSRC bit in the PWMnCTL register must be set for the bit to affect fault condition generation.	าis		
0	FAULT0	R/W	0	Fault0 Input			
				Value Description			
				0 The Fault0 signal is suppressed and cannot generate a fau condition.	ılt		
				1 The Fault0 signal value is ORed with all other fault condition generation inputs (Faultn signals and digital comparators).			
				Note: The FLTSRC bit in the PWMnCTL register must be set for the bit to affect fault condition generation.	nis		

Register 68: PWM0 Fault Source 1 (PWM0FLTSRC1), offset 0x078

Register 69: PWM1 Fault Source 1 (PWM1FLTSRC1), offset 0x0B8

Register 70: PWM2 Fault Source 1 (PWM2FLTSRC1), offset 0x0F8

Register 71: PWM3 Fault Source 1 (PWM3FLTSRC1), offset 0x138


This register specifies which digital comparator triggers from the ADC are used to generate a fault condition. Each bit in the following register indicates whether the corresponding digital comparator trigger is included in the fault condition. All enabled digital comparator triggers are ORed together to form the **PWMnFLTSRC1** portion of the fault condition. The **PWMnFLTSRC1** fault condition is then ORed with the **PWMnFLTSRC0** fault condition to generate the final fault condition for the PWM generator.

If the FLTSRC bit in the **PWMnCTL** register (see page 1274) is clear, only the PWM Fault0 pin affects the fault condition generated. Otherwise, sources defined in **PWMnFLTSRC0** and **PWMnFLTSRC1** affect the fault condition generated.

PWMn Fault Source 1 (PWMnFLTSRC1)

PWM0 base: 0x4002.8000 PWM1 base: 0x4002.9000 Offset 0x078

Type R/W, reset 0x0000.0000



Bit/Field	Name	Type	Reset	Description
31:8	reserved	RO	0x0000.00	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
7	DCMP7	R/W	0	Digital Comparator 7

Value Description

- The trigger from digital comparator 7 is suppressed and cannot generate a fault condition.
- 1 The trigger from digital comparator 7 is ORed with all other fault condition generation inputs (Faultn signals and digital comparators).

Note: The FLTSRC bit in the **PWMnCTL** register must be set for this bit to affect fault condition generation.

Bit/Field	Name	Туре	Reset	Description
6	DCMP6	R/W	0	Digital Comparator 6
				Value Description
				The trigger from digital comparator 6 is suppressed and cannot generate a fault condition.
				1 The trigger from digital comparator 6 is ORed with all other fault condition generation inputs (Faultn signals and digital comparators).
				Note: The FLTSRC bit in the PWMnCTL register must be set for this bit to affect fault condition generation.
5	DCMP5	R/W	0	Digital Comparator 5
				Value Description
				The trigger from digital comparator 5 is suppressed and cannot generate a fault condition.
				1 The trigger from digital comparator 5 is ORed with all other fault condition generation inputs (Faultn signals and digital comparators).
				Note: The FLTSRC bit in the PWMnCTL register must be set for this bit to affect fault condition generation.
4	DCMP4	R/W	0	Digital Comparator 4
				Value Description
				The trigger from digital comparator 4 is suppressed and cannot generate a fault condition.
				1 The trigger from digital comparator 4 is ORed with all other fault condition generation inputs (Faultn signals and digital comparators).
				Note: The FLTSRC bit in the PWMnCTL register must be set for this bit to affect fault condition generation.
3	DCMP3	R/W	0	Digital Comparator 3
				Value Description
				The trigger from digital comparator 3 is suppressed and cannot generate a fault condition.
				1 The trigger from digital comparator 3 is ORed with all other fault condition generation inputs (Faultn signals and digital comparators).
				Note: The FLTSRC bit in the PWMnCTL register must be set for this bit to affect fault condition generation.

Bit/Field	Name	Туре	Reset	Description
2	DCMP2	R/W	0	Digital Comparator 2
				Value Description
				The trigger from digital comparator 2 is suppressed and cannot generate a fault condition.
				1 The trigger from digital comparator 2 is ORed with all other fault condition generation inputs (Faultn signals and digital comparators).
				Note: The FLTSRC bit in the PWMnCTL register must be set for this bit to affect fault condition generation.
1	DCMP1	R/W	0	Digital Comparator 1
				Value Description
				The trigger from digital comparator 1 is suppressed and cannot generate a fault condition.
				1 The trigger from digital comparator 1 is ORed with all other fault condition generation inputs (Faultn signals and digital comparators).
				Note: The FLTSRC bit in the PWMnCTL register must be set for this bit to affect fault condition generation.
0	DCMP0	R/W	0	Digital Comparator 0
				Value Description
				0 The trigger from digital comparator 0 is suppressed and cannot generate a fault condition.
				The trigger from digital comparator 0 is ORed with all other fault condition generation inputs (Faultn signals and digital comparators).
				Note: The FLTSRC bit in the PWMnCTL register must be set for this bit to affect fault condition generation.


Register 72: PWM0 Minimum Fault Period (PWM0MINFLTPER), offset 0x07C Register 73: PWM1 Minimum Fault Period (PWM1MINFLTPER), offset 0x0BC Register 74: PWM2 Minimum Fault Period (PWM2MINFLTPER), offset 0x0FC Register 75: PWM3 Minimum Fault Period (PWM3MINFLTPER), offset 0x13C

If the MINFLTPER bit in the **PWMnCTL** register is set, this register specifies the 16-bit time-extension value to be used in extending the fault condition. The value is loaded into a 16-bit down counter, and the counter value is used to extend the fault condition. The fault condition is released in the clock immediately after the counter value reaches 0. The fault condition is asynchronous to the PWM clock; and the delay value is the product of the PWM clock period and the (MFP field value + 1) or (MFP field value + 2) depending on when the fault condition asserts with respect to the PWM clock. The counter decrements at the PWM clock rate, without pause or condition.

PWMn Minimum Fault Period (PWMnMINFLTPER)

PWM0 base: 0x4002.8000 PWM1 base: 0x4002.9000 Offset 0x07C

Type R/W, reset 0x0000.0000



Bit/Field	Name	Type	Reset	Description
31:16	reserved	RO	0x0000	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
15:0	MFP	R/W	0x0000	Minimum Fault Period

The number of PWM clocks by which a fault condition is extended when the delay is enabled by ${\bf PWMnCTL}$ MINFLTPER.

20

19

18

16

Register 76: PWM0 Fault Pin Logic Sense (PWM0FLTSEN), offset 0x800 Register 77: PWM1 Fault Pin Logic Sense (PWM1FLTSEN), offset 0x880 Register 78: PWM2 Fault Pin Logic Sense (PWM2FLTSEN), offset 0x900 Register 79: PWM3 Fault Pin Logic Sense (PWM3FLTSEN), offset 0x980

23

This register defines the PWM fault pin logic sense.

26

PWMn Fault Pin Logic Sense (PWMnFLTSEN)

29

28

PWM0 base: 0x4002.8000 PWM1 base: 0x4002.9000

Offset 0x800

Type R/W, reset 0x0000.0000

30

	31	30	29		21	20	25	24	23		21	20	19	10	17	16
								rese	erved		1	I				
Type L	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO
Reset	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0
	15	14	13	12	11	10	9	8	7	6	5	4	3	2	1	0
						re	served			•			FAULT3	FAULT2	FAULT1	FAULT0
Type Reset	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	R/W 0	R/W 0	R/W 0	R/W 0
110001	Ü	Ü	Ü	Ü	Ü	Ü	Ü	Ü	Ü	Ü	Ü	Ü	Ü	Ü	Ü	Ü
В	sit/Field		Nam	ne	Тур	е	Reset	Des	cription							
	31:4		reserv	ved	RC)	0x0000.000	Soft	ware sh	ould not	relv on tl	he value	of a res	erved bit	. To prov	vide
								com	patibility	with futu	ure produ	ucts, the	value of	a reserv		
								pres	served a	cross a r	ead-mod	dify-write	operation	n.		
	3		FAUL	.T3	R/V	V	0	Fau	lt3 Sens	е						
								Val	ue Des	cription						
								0	An e	rror is in	dicated it	f the Fau	ılt3 sig	nal is Hig	gh.	
								1	An e	rror is in	dicated it	f the Fau	ılt3 sig	nal is Lo	W.	
	2		FAUL	.T2	R/V	V	0	Fau	lt2 Sens	е						
								Val	ue Des	cription						
								0	An e	rror is in	dicated it	f the Fau	ılt2 sig	nal is Hig	gh.	
								1	An e	rror is in	dicated if	f the Fau	ılt2 sig	nal is Lo	W.	
	1		FAUL	.T1	R/V	V	0	Fau	lt1 Sens	е						
								Val	ue Des	cription						
								0	An e	rror is in	dicated it	f the Fau	ılt1 sig	nal is Hig	gh.	
								1	An e	rror is in	dicated if	f the Fat	ılt1 sig	nal is Lo	W.	
								_								
	0		FAUL	-10	R/V	V	0	⊦au	lt0 Sens	е						
								Val	ue Des	cription						
								0	An e	rror is in	dicated if	f the Fau	ılt0 sig	nal is Hig	gh.	
								1	An e	rror is in	dicated it	f the Faເ	ılt0 sig	nal is Lo	W.	

Register 80: PWM0 Fault Status 0 (PWM0FLTSTAT0), offset 0x804

Register 81: PWM1 Fault Status 0 (PWM1FLTSTAT0), offset 0x884

Register 82: PWM2 Fault Status 0 (PWM2FLTSTAT0), offset 0x904

Register 83: PWM3 Fault Status 0 (PWM3FLTSTAT0), offset 0x984

Along with the **PWMnFLTSTAT1** register, this register provides status regarding the fault condition inputs.

If the LATCH bit in the **PWMnCTL** register is clear, the contents of the **PWMnFLTSTAT0** register are read-only (RO) and provide the current state of the MnFAULTn inputs.


If the LATCH bit in the **PWMnCTL** register is set, the contents of the **PWMnFLTSTAT0** register are read / write 1 to clear (R/W1C) and provide a latched version of the MnFAULTn inputs. In this mode, the register bits are cleared by writing a 1 to a set bit. The MnFAULTn inputs are recorded after their sense is adjusted in the generator.

The contents of this register can only be written if the fault source extensions are enabled (the FLTSRC bit in the **PWMnCTL** register is set).

PWMn Fault Status 0 (PWMnFLTSTAT0)

PWM0 base: 0x4002.8000 PWM1 base: 0x4002.9000 Offset 0x804

Type -, reset 0x0000.0000



Bit/Field	Name	Туре	Reset	Description
31:4	reserved	RO	0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
3	FAULT3	-	0	Fault Input 3

If the **PWMnCTL** register LATCH bit is clear, this bit is RO and represents the current state of the ${\tt MnFAULT3}$ input signal after the logic sense adjustment.

If the **PWMnCTL** register LATCH bit is set, this bit is R/W1C and represents a sticky version of the MnFAULT3 input signal after the logic sense adjustment.

- If FAULT3 is set, the input transitioned to the active state previously.
- If FAULT3 is clear, the input has not transitioned to the active state since the last time it was cleared.
- The FAULT3 bit is cleared by writing it with the value 1.

Bit/Field	Name	Туре	Reset	Description
2	FAULT2	-	0	Fault Input 2 If the PWMnCTL register LATCH bit is clear, this bit is RO and represents the current state of the MnFAULT2 input signal after the logic sense adjustment. If the PWMnCTL register LATCH bit is set, this bit is R/W1C and represents a sticky version of the MnFAULT2 input signal after the logic sense adjustment. If FAULT2 is set, the input transitioned to the active state previously.
				 If FAULT2 is clear, the input has not transitioned to the active state since the last time it was cleared.
				■ The FAULT2 bit is cleared by writing it with the value 1.
1	FAULT1	-	0	Fault Input 1 If the PWMnCTL register LATCH bit is clear, this bit is RO and represents the current state of the MnFAULT1 input signal after the logic sense adjustment. If the PWMnCTL register LATCH bit is set, this bit is R/W1C and represents a sticky version of the MnFAULT1 input signal after the logic sense adjustment. If FAULT1 is set, the input transitioned to the active state previously. If FAULT1 is clear, the input has not transitioned to the active state since the last time it was cleared. The FAULT1 bit is cleared by writing it with the value 1.
0	FAULT0	-	0	Fault Input 0 If the PWMnCTL register LATCH bit is clear, this bit is RO and represents the current state of the input signal after the logic sense adjustment. If the PWMnCTL register LATCH bit is set, this bit is R/W1C and represents a sticky version of the input signal after the logic sense adjustment. If FAULTO is set, the input transitioned to the active state previously. If FAULTO is clear, the input has not transitioned to the active state since the last time it was cleared. The FAULTO bit is cleared by writing it with the value 1.

February 20, 2013 1307

Register 84: PWM0 Fault Status 1 (PWM0FLTSTAT1), offset 0x808

Register 85: PWM1 Fault Status 1 (PWM1FLTSTAT1), offset 0x888

Register 86: PWM2 Fault Status 1 (PWM2FLTSTAT1), offset 0x908

Register 87: PWM3 Fault Status 1 (PWM3FLTSTAT1), offset 0x988

Along with the **PWMnFLTSTAT0** register, this register provides status regarding the fault condition inputs.


If the LATCH bit in the PWMnCTL register is clear, the contents of the PWMnFLTSTAT1 register are read-only (RO) and provide the current state of the digital comparator triggers.

If the LATCH bit in the PWMnCTL register is set, the contents of the PWMnFLTSTAT1 register are read / write 1 to clear (R/W1C) and provide a latched version of the digital comparator triggers. In this mode, the register bits are cleared by writing a 1 to a set bit. The contents of this register can only be written if the fault source extensions are enabled (the FLTSRC bit in the PWMnCTL register is set).

PWMn Fault Status 1 (PWMnFLTSTAT1)

PWM0 base: 0x4002.8000 PWM1 base: 0x4002.9000 Offset 0x808

Type -, reset 0x0000.0000



Bit/Field	Name	Туре	Reset	Description
31:8	reserved	RO	0x0000.00	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
7	DCMP7	_	0	Digital Comparator 7 Trigger

If the PWMnCTL register LATCH bit is clear, this bit represents the current state of the Digital Comparator 7 trigger input.

If the PWMnCTL register LATCH bit is set, this bit represents a sticky version of the trigger.

- If DCMP7 is set, the trigger transitioned to the active state previously.
- If DCMP7 is clear, the trigger has not transitioned to the active state since the last time it was cleared.
- The DCMP7 bit is cleared by writing it with the value 1.

Bit/Field	Name	Туре	Reset	Description
6	DCMP6	-	0	Digital Comparator 6 Trigger If the PWMnCTL register LATCH bit is clear, this bit represents the current state of the Digital Comparator 6 trigger input. If the PWMnCTL register LATCH bit is set, this bit represents a sticky version of the trigger. If DCMP6 is set, the trigger transitioned to the active state previously. If DCMP6 is clear, the trigger has not transitioned to the active state since the last time it was cleared. The DCMP6 bit is cleared by writing it with the value 1.
5	DCMP5	-	0	Digital Comparator 5 Trigger If the PWMnCTL register LATCH bit is clear, this bit represents the current state of the Digital Comparator 5 trigger input. If the PWMnCTL register LATCH bit is set, this bit represents a sticky version of the trigger. If DCMP5 is set, the trigger transitioned to the active state previously. If DCMP5 is clear, the trigger has not transitioned to the active state since the last time it was cleared. The DCMP5 bit is cleared by writing it with the value 1.
4	DCMP4	-	0	Digital Comparator 4 Trigger If the PWMnCTL register LATCH bit is clear, this bit represents the current state of the Digital Comparator 4 trigger input. If the PWMnCTL register LATCH bit is set, this bit represents a sticky version of the trigger. If DCMP4 is set, the trigger transitioned to the active state previously. If DCMP4 is clear, the trigger has not transitioned to the active state since the last time it was cleared. The DCMP4 bit is cleared by writing it with the value 1.
3	DCMP3	-	0	Digital Comparator 3 Trigger If the PWMnCTL register LATCH bit is clear, this bit represents the current state of the Digital Comparator 3 trigger input. If the PWMnCTL register LATCH bit is set, this bit represents a sticky version of the trigger. If DCMP3 is set, the trigger transitioned to the active state previously. If DCMP3 is clear, the trigger has not transitioned to the active state since the last time it was cleared. The DCMP3 bit is cleared by writing it with the value 1.

February 20, 2013 1309

Bit/Field	Name	Туре	Reset	Description
2	DCMP2	-	0	Digital Comparator 2 Trigger If the PWMnCTL register LATCH bit is clear, this bit represents the current state of the Digital Comparator 2 trigger input. If the PWMnCTL register LATCH bit is set, this bit represents a sticky version of the trigger. If DCMP2 is set, the trigger transitioned to the active state previously. If DCMP2 is clear, the trigger has not transitioned to the active state since the last time it was cleared. The DCMP2 bit is cleared by writing it with the value 1.
1	DCMP1	-	0	Digital Comparator 1 Trigger If the PWMnCTL register LATCH bit is clear, this bit represents the current state of the Digital Comparator 1 trigger input. If the PWMnCTL register LATCH bit is set, this bit represents a sticky version of the trigger. If DCMP1 is set, the trigger transitioned to the active state previously. If DCMP1 is clear, the trigger has not transitioned to the active state since the last time it was cleared. The DCMP1 bit is cleared by writing it with the value 1.
0	DCMP0	-	0	Digital Comparator 0 Trigger If the PWMnCTL register LATCH bit is clear, this bit represents the current state of the Digital Comparator 0 trigger input. If the PWMnCTL register LATCH bit is set, this bit represents a sticky version of the trigger. If DCMP0 is set, the trigger transitioned to the active state previously. If DCMP0 is clear, the trigger has not transitioned to the active state since the last time it was cleared. The DCMP0 bit is cleared by writing it with the value 1.

1310 February 20, 2013

Register 88: PWM Peripheral Properties (PWMPP), offset 0xFC0

The **PWMPP** register provides information regarding the properties of the PWM module.

PWM Peripheral Properties (PWMPP)

PWM0 base: 0x4002.8000 PWM1 base: 0x4002.9000 Offset 0xFC0

Type RO, reset 0x0000.0344

. , , , ,	24	20	20	20	27	26	25	24	22	22	24	20	10	10	17	10
Γ	31	30	29	28	27	26	25	24	23 rved	22	21	20	19 T	18	17 I	16
Type	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO	RO
Type Reset	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0
	15	14	13	12	11	10	9	8	7	6	5	4	3	2	1	0
			reserved			ONE	EFAULT	ESYNC		FC	CNT	1		GC	CNT	'
Type Reset	RO 0	RO 0	RO 0	RO 0	RO 0	RO 0	RO 1	RO 1	RO 0	RO 1	RO 0	RO 0	RO 0	RO 1	RO 0	RO 0
В	Bit/Field		Nam	е	Ту	ре	Reset	Des	cription							
	31:11		reserv	red	R	.0	0x0	com	patibility	with fut	ure prod		value of	a reserv	t. To prov ved bit sh	
	10		ONE	≣	R	.0	0x0	One	-Shot M	ode						
								Valu	ue Desc	cription						
								0	One	shot mo	des are	not avail	able.			
								1	One	-shot mo	des are	available) .			
	9		EFAU	LT	R	.0	0x1	Exte	ended Fa	ault						
								Valu	ue Desc	cription						
								0			ılt capab	ilities are	not ava	ilable.		
								1	Exte	nded fau	ılt capab	ilities are	availab	le.		
	8		ESYN	IC	R	0	0x1	Exte	ended S	ynchroni	zation					
								Valu	ue Desc	cription						
								0			nchroniza	ation is n	ot availa	able.		
								1		-		ation is a				
	7:4		FCN	Т	R	.0	0x4	Fau	It Inputs							
								Valu	је Г	Description	nn .					
								0x0		lo fault in						
								0x1		fault inp	•					
								0x2		fault inp						
								0x3		fault inp						
								0x4	4	fault inp	out.					
								0x5	- 0xF r	eserved						

Bit/Field	Name	Type	Reset	Descriptio	n
3:0	GCNT	RO	0x4	Generator	S
				Value	Description
				0x0	No generators.
				0x1	1 generator
				0x2	2 generators
				0x3	3 generators
				0x4	4 generators
				0x5 - 0xF	reserved

The number of PWM outputs is 2 times the number of PWM generators.

21 Quadrature Encoder Interface (QEI)

A quadrature encoder, also known as a 2-channel incremental encoder, converts linear displacement into a pulse signal. By monitoring both the number of pulses and the relative phase of the two signals, you can track the position, direction of rotation, and speed. In addition, a third channel, or index signal, can be used to reset the position counter.

The LM4F232H5QC microcontroller includes two quadrature encoder interface (QEI) modules. Each QEI module interprets the code produced by a quadrature encoder wheel to integrate position over time and determine direction of rotation. In addition, it can capture a running estimate of the velocity of the encoder wheel.

The Stellaris[®] LM4F232H5QC microcontroller includes two QEI modules providing control of two motors at the same time with the following features:

- Position integrator that tracks the encoder position
- Programmable noise filter on the inputs
- Velocity capture using built-in timer
- The input frequency of the QEI inputs may be as high as 1/4 of the processor frequency (for example, 12.5 MHz for a 50-MHz system)
- Interrupt generation on:
 - Index pulse
 - Velocity-timer expiration
 - Direction change
 - Quadrature error detection

21.1 Block Diagram

Figure 21-1 on page 1314 provides a block diagram of a Stellaris QEI module.

PhA INVA QEILOAD Control & Status Velocity Timer QEITIME QEICTL Velocity Accumulator Velocity QEICOUNT QEISPEED Predivider INVR SWAP IntPh/ clk QEIMAXPOS Quadrature Position Integrator IntPhB Encoder QEIPOS IDX **SWAP** QEIINTEN Interrupt Control Interrupt QEIRIS

Figure 21-1. QEI Block Diagram

21.2 Signal Description

The following table lists the external signals of the QEI module and describes the function of each. The QEI signals are alternate functions for some GPIO signals and default to be GPIO signals at reset. The column in the table below titled "Pin Mux/Pin Assignment" lists the possible GPIO pin placements for these QEI signals. The AFSEL bit in the **GPIO Alternate Function Select** (**GPIOAFSEL**) register (page 670) should be set to choose the QEI function. The number in parentheses is the encoding that must be programmed into the PMCn field in the **GPIO Port Control** (**GPIOPCTL**) register (page 688) to assign the QEI signal to the specified GPIO port pin. For more information on configuring GPIOs, see "General-Purpose Input/Outputs (GPIOs)" on page 646.

Table 21-1. QEI Signals (100LQFP)

Pin Name	Pin Number	Pin Mux / Pin Assignment	Pin Type	Buffer Type ^a	Description
IDX0	4 11 17 39	PD3 (6) PJ2 (5) PH1 (5) PF4 (6)	I	TTL	QEI module 0 index.
IDX1	25 75 88	PC4 (6) PG5 (6) PG7 (5)	I	TTL	QEI module 1 index.
PhA0	40 79 99	PF0 (6) PH4 (5) PD6 (6)	I	TTL	QEI module 0 phase A.

Pin Name	Pin Number	Pin Mux / Pin Assignment	Pin Type	Buffer Type ^a	Description
PhA1	24	PC5 (6)	I	TTL	QEI module 1 phase A.
	59	PG3 (6)			
	62	PG0 (6)			
PhB0	41	PF1 (6)	I	TTL	QEI module 0 phase B.
	78	PH5 (5)			
	100	PD7 (6)			
PhB1	23	PC6 (6)	1	TTL	QEI module 1 phase B.
	61	PG1 (6)			
	74	PG4 (6)			

Table 21-1. QEI Signals (100LQFP) (continued)

21.3 Functional Description

The QEI module interprets the two-bit gray code produced by a quadrature encoder wheel to integrate position over time and determine direction of rotation. In addition, it can capture a running estimate of the velocity of the encoder wheel.

The position integrator and velocity capture can be independently enabled, though the position integrator must be enabled before the velocity capture can be enabled. The two phase signals, PhA and PhB, can be swapped before being interpreted by the QEI module to change the meaning of forward and backward and to correct for miswiring of the system. Alternatively, the phase signals can be interpreted as a clock and direction signal as output by some encoders.

The QEI module input signals have a digital noise filter on them that can be enabled to prevent spurious operation. The noise filter requires that the inputs be stable for a specified number of consecutive clock cycles before updating the edge detector. The filter is enabled by the FILTEN bit in the QEI Control (QEICTL) register. The frequency of the input update is programmable using the FILTCNT bit field in the QEICTL register.

The QEI module supports two modes of signal operation: quadrature phase mode and clock/direction mode. In quadrature phase mode, the encoder produces two clocks that are 90 degrees out of phase; the edge relationship is used to determine the direction of rotation. In clock/direction mode, the encoder produces a clock signal to indicate steps and a direction signal to indicate the direction of rotation. This mode is determined by the SIGMODE bit of the **QEICTL** register (see page 1319).

When the QEI module is set to use the quadrature phase mode (SIGMODE bit is clear), the capture mode for the position integrator can be set to update the position counter on every edge of the PhA signal or to update on every edge of both PhA and PhB. Updating the position counter on every PhA and PhB edge provides more positional resolution at the cost of less range in the positional counter.

When edges on PhA lead edges on PhB, the position counter is incremented. When edges on PhB lead edges on PhA, the position counter is decremented. When a rising and falling edge pair is seen on one of the phases without any edges on the other, the direction of rotation has changed.

The positional counter is automatically reset on one of two conditions: sensing the index pulse or reaching the maximum position value. The reset mode is determined by the RESMODE bit of the **QEICTL** register.

When RESMODE is set, the positional counter is reset when the index pulse is sensed. This mode limits the positional counter to the values [0:N-1], where N is the number of phase edges in a full revolution of the encoder wheel. The **QEI Maximum Position (QEIMAXPOS)** register must be programmed with N-1 so that the reverse direction from position 0 can move the position counter

a. The TTL designation indicates the pin has TTL-compatible voltage levels.


to N-1. In this mode, the position register contains the absolute position of the encoder relative to the index (or home) position once an index pulse has been seen.

When RESMODE is clear, the positional counter is constrained to the range [0:M], where M is the programmable maximum value. The index pulse is ignored by the positional counter in this mode.

Velocity capture uses a configurable timer and a count register. The timer counts the number of phase edges (using the same configuration as for the position integrator) in a given time period. The edge count from the previous time period is available to the controller via the **QEI Velocity** (**QEISPEED**) register, while the edge count for the current time period is being accumulated in the **QEI Velocity Counter** (**QEICOUNT**) register. As soon as the current time period is complete, the total number of edges counted in that time period is made available in the **QEISPEED** register (overwriting the previous value), the **QEICOUNT** register is cleared, and counting commences on a new time period. The number of edges counted in a given time period is directly proportional to the velocity of the encoder.

Figure 21-2 on page 1316 shows how the Stellaris quadrature encoder converts the phase input signals into clock pulses, the direction signal, and how the velocity predivider operates (in Divide by 4 mode).

Figure 21-2. Quadrature Encoder and Velocity Predivider Operation



The period of the timer is configurable by specifying the load value for the timer in the **QEI Timer Load (QEILOAD)** register. When the timer reaches zero, an interrupt can be triggered, and the hardware reloads the timer with the **QEILOAD** value and continues to count down. At lower encoder speeds, a longer timer period is required to be able to capture enough edges to have a meaningful result. At higher encoder speeds, both a shorter timer period and/or the velocity predivider can be used.

The following equation converts the velocity counter value into an rpm value:

```
rpm = (clock * (2 ^ VELDIV) * SPEED * 60) ÷ (LOAD * ppr * edges)
where:
```

clock is the controller clock rate

ppr is the number of pulses per revolution of the physical encoder

edges is 2 or 4, based on the capture mode set in the **QEICTL** register (2 for CAPMODE clear and 4 for CAPMODE set)

For example, consider a motor running at 600 rpm. A 2048 pulse per revolution quadrature encoder is attached to the motor, producing 8192 phase edges per revolution. With a velocity predivider of ÷1 (VELDIV is clear) and clocking on both PhA and PhB edges, this results in 81,920 pulses per second (the motor turns 10 times per second). If the timer were clocked at 10,000 Hz, and the load value was 2,500 (¼ of a second), it would count 20,480 pulses per update. Using the above equation:

$$rpm = (10000 * 1 * 20480 * 60) \div (2500 * 2048 * 4) = 600 rpm$$

Now, consider that the motor is sped up to 3000 rpm. This results in 409,600 pulses per second, or 102,400 every $\frac{1}{4}$ of a second. Again, the above equation gives:

```
rpm = (10000 * 1 * 102400 * 60) \div (2500 * 2048 * 4) = 3000 rpm
```

Care must be taken when evaluating this equation because intermediate values may exceed the capacity of a 32-bit integer. In the above examples, the clock is 10,000 and the divider is 2,500; both could be predivided by 100 (at compile time if they are constants) and therefore be 100 and 25. In fact, if they were compile-time constants, they could also be reduced to a simple multiply by 4, cancelled by the ÷4 for the edge-count factor.

Important: Reducing constant factors at compile time is the best way to control the intermediate values of this equation and reduce the processing requirement of computing this equation.

The division can be avoided by selecting a timer load value such that the divisor is a power of 2; a simple shift can therefore be done in place of the division. For encoders with a power of 2 pulses per revolution, the load value can be a power of 2. For other encoders, a load value must be selected such that the product is very close to a power of 2. For example, a 100 pulse-per-revolution encoder could use a load value of 82, resulting in 32,800 as the divisor, which is 0.09% above 2¹⁴. In this case a shift by 15 would be an adequate approximation of the divide in most cases. If absolute accuracy were required, the microcontroller's divide instruction could be used.

The QEI module can produce a controller interrupt on several events: phase error, direction change, reception of the index pulse, and expiration of the velocity timer. Standard masking, raw interrupt status, interrupt status, and interrupt clear capabilities are provided.

21.4 Initialization and Configuration

The following example shows how to configure the Quadrature Encoder module to read back an absolute position:

- 1. Enable the QEI clock using the **RCGCQEI** register in the System Control module (see page 346).
- **2.** Enable the clock to the appropriate GPIO module via the **RCGCGPIO** register in the System Control module (see page 330).
- 3. In the GPIO module, enable the appropriate pins for their alternate function using the **GPIOAFSEL** register. To determine which GPIOs to configure, see Table 23-4 on page 1358.
- **4.** Configure the PMCn fields in the **GPIOPCTL** register to assign the QEI signals to the appropriate pins (see page 688 and Table 23-5 on page 1367).
- **5.** Configure the quadrature encoder to capture edges on both signals and maintain an absolute position by resetting on index pulses. A 1000-line encoder with four edges per line, results in 4000 pulses per revolution; therefore, set the maximum position to 3999 (0xF9F) as the count is zero-based.
 - Write the **QEICTL** register with the value of 0x0000.0018.
 - Write the **QEIMAXPOS** register with the value of 0x0000.0F9F.
- **6.** Enable the quadrature encoder by setting bit 0 of the **QEICTL** register.

Note: Once the QEI module has been enabled by setting the ENABLE bit in the QEICTL register, it cannot be disabled. The only way to clear the ENABLE bit is to reset the module using the Quadrature Encoder Interface Software Reset (SRQEI) register.

- 7. Delay until the encoder position is required.
- 8. Read the encoder position by reading the QEI Position (QEIPOS) register value.

21.5 Register Map

Table 21-2 on page 1318 lists the QEI registers. The offset listed is a hexadecimal increment to the register's address, relative to the module's base address:

QEI0: 0x4002.C000QEI1: 0x4002.D000

Note that the QEI module clock must be enabled before the registers can be programmed (see page 346). There must be a delay of 3 system clocks after the QEI module clock is enabled before any QEI module registers are accessed.

Table 21-2. QEI Register Map

Offset	Name	Туре	Reset	Description	See page
0x000	QEICTL	R/W	0x0000.0000	QEI Control	1319
0x004	QEISTAT	RO	0x0000.0000	QEI Status	1322
0x008	QEIPOS	R/W	0x0000.0000	QEI Position	1323
0x00C	QEIMAXPOS	R/W	0x0000.0000	QEI Maximum Position	1324
0x010	QEILOAD	R/W	0x0000.0000	QEI Timer Load	1325
0x014	QEITIME	RO	0x0000.0000	QEI Timer	1326
0x018	QEICOUNT	RO	0x0000.0000	QEI Velocity Counter	1327
0x01C	QEISPEED	RO	0x0000.0000	QEI Velocity	1328
0x020	QEIINTEN	R/W	0x0000.0000	QEI Interrupt Enable	1329
0x024	QEIRIS	RO	0x0000.0000	QEI Raw Interrupt Status	1331
0x028	QEIISC	R/W1C	0x0000.0000	QEI Interrupt Status and Clear	1333

21.6 Register Descriptions

The remainder of this section lists and describes the QEI registers, in numerical order by address offset.

Register 1: QEI Control (QEICTL), offset 0x000


This register contains the configuration of the QEI module. Separate enables are provided for the quadrature encoder and the velocity capture blocks; the quadrature encoder must be enabled in order to capture the velocity, but the velocity does not need to be captured in applications that do not need it. The phase signal interpretation, phase swap, Position Update mode, Position Reset mode, and velocity predivider are all set via this register.

QEI Control (QEICTL)

QEI0 base: 0x4002.C000 QEI1 base: 0x4002.D000

Offset 0x000

Type R/W, reset 0x0000.0000



Bit/Field	Name	Туре	Reset	Description
31:20	reserved	RO	0x000	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
19:16	FILTCNT	R/W	0x0	Input Filter Prescale Count
				This field controls the frequency of the input update.
				When this field is clear, the input is sampled after 2 system clocks. When this field ix 0x1, the input is sampled after 3 system clocks. Similarly, when this field is 0xF, the input is sampled after 17 clocks.
15:14	reserved	RO	0x0	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
13	FILTEN	R/W	0	Enable Input Filter
				Value Description
				0 The QEI inputs are not filtered.
				Enables the digital noise filter on the QEI input signals. Inputs must be stable for 3 consecutive clock edges before the edge detector is updated.
12	STALLEN	R/W	0	Stall QEI

Value Description

- The QEI module does not stall when the microcontroller is stopped by a debugger.
- The QEI module stalls when the microcontroller is stopped by a debugger.

Bit/Field	Name	Туре	Reset	Description
11	INVI	R/W	0	Invert Index Pulse
				Value Description
				0 No effect.
				1 Inverts the IDX input.
10	INVB	R/W	0	Invert PhB
				Value Description
				0 No effect.
				1 Inverts the PhB input.
9	INVA	R/W	0	Invert PhA
				Value Description
				0 No effect.
				1 Inverts the PhA input.
8:6	VELDIV	R/W	0x0	Predivide Velocity
0.0	VLLDIV	IVV	OXO	This field defines the predivider of the input quadrature pulses before
				being applied to the QEICOUNT accumulator.
				Value Predivider
				0x0 ÷1
				0x1 ÷2
				0x2 ÷4
				0x3 ÷8
				0x4 ÷16
				0x5 ÷32
				0x6 ÷64
				0x7 ÷128
5	VELEN	R/W	0	Capture Velocity
				Value Description
				0 No effect.
				1 Enables capture of the velocity of the quadrature encoder.
4	RESMODE	R/W	0	Reset Mode
				Value Description
				O The position counter is reset when it reaches the maximum as defined by the MAXPOS field in the QEIMAXPOS register.
				1 The position counter is reset when the index pulse is captured.

Bit/Field	Name	Туре	Reset	Description
3	CAPMODE	R/W	0	Capture Mode
				Note: When SIGMODE=1, the CAPMODE setting is not applicable and is reserved.
				Value Description
				Only the PhA edges are counted.
				The PhA and PhB edges are counted, providing twice the positional resolution but half the range.
2	SIGMODE	R/W	0	Signal Mode
				Value Description
				0 The PhA and PhB signals operate as quadrature phase signals.
				The internal PhA (IntPhA) signal (post swap and inversion) operates as the clock (CLK) signal and the internal PhB (IntPhB) signal (post swap and inversion) operates as the direction (DIR) signal
1	SWAP	R/W	0	Swap Signals
				Note if the ${\tt INVA}$ or ${\tt INVB}$ bit are set, the inversion of the signals will occur prior to the swap.
				Value Description
				0 No effect.
				1 Swaps the PhA and PhB signals.
0	ENABLE	R/W	0	Enable QEI
				Value Description
				0 No effect.
				1 Enables the quadrature encoder module.
				Note: Once the QEI module has been enabled by setting the ENABLE bit, it cannot be disabled. The only way to clear the ENABLE bit is to reset the module using the Quadrature Encoder Interface Software Reset (SRQEI) register.

February 20, 2013 1321


Register 2: QEI Status (QEISTAT), offset 0x004

This register provides status about the operation of the QEI module.

QEI Status (QEISTAT)

QEI0 base: 0x4002.C000 QEI1 base: 0x4002.D000 Offset 0x004

Type RO, reset 0x0000.0000



Bit/Field	Name	Туре	Reset	Description
31:2	reserved	RO	0x0000.000	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
1	DIRECTION	RO	0	Direction of Rotation Indicates the direction the encoder is rotating. Value Description
				The encoder is rotating forward.
				1 The encoder is rotating in reverse.
0	ERROR	RO	0	Error Detected

Value Description

0 No error.

An error was detected in the gray code sequence (that is, both signals changing at the same time).

Register 3: QEI Position (QEIPOS), offset 0x008

This register contains the current value of the position integrator. The value is updated by the status of the QEI phase inputs and can be set to a specific value by writing to it.

0x0000.0000 Current Position Integrator Value


QEI Position (QEIPOS)

QEI0 base: 0x4002.C000 QEI1 base: 0x4002.D000 Offset 0x008

31:0

POSITION

R/W



The current value of the position integrator.

Register 4: QEI Maximum Position (QEIMAXPOS), offset 0x00C


This register contains the maximum value of the position integrator. When moving forward, the position register resets to zero when it increments past this value. When moving in reverse, the position register resets to this value when it decrements from zero.

QEI Maximum Position (QEIMAXPOS)

QEI0 base: 0x4002.C000 QEI1 base: 0x4002.D000

Offset 0x00C

Type R/W, reset 0x0000.0000



The maximum value of the position integrator.


Register 5: QEI Timer Load (QEILOAD), offset 0x010

This register contains the load value for the velocity timer. Because this value is loaded into the timer on the clock cycle after the timer is zero, this value should be one less than the number of clocks in the desired period. So, for example, to have 2000 decimal clocks per timer period, this register should contain 1999 decimal.

QEI Timer Load (QEILOAD)

QEI0 base: 0x4002.C000 QEI1 base: 0x4002.D000 Offset 0x010

Type R/W, reset 0x0000.0000



The load value for the velocity timer.

Register 6: QEI Timer (QEITIME), offset 0x014


This register contains the current value of the velocity timer. This counter does not increment when the VELEN bit in the **QEICTL** register is clear.

QEI Timer (QEITIME)

QEI0 base: 0x4002.C000 QEI1 base: 0x4002.D000

Offset 0x014

Type RO, reset 0x0000.0000



31:0 TIME RO 0x0000.0000 Velocity Timer Current Value


The current value of the velocity timer.

Register 7: QEI Velocity Counter (QEICOUNT), offset 0x018

This register contains the running count of velocity pulses for the current time period. Because this count is a running total, the time period to which it applies cannot be known with precision (that is, a read of this register does not necessarily correspond to the time returned by the **QEITIME** register because there is a small window of time between the two reads, during which either value may have changed). The **QEISPED** register should be used to determine the actual encoder velocity; this register is provided for information purposes only. This counter does not increment when the VELEN bit in the **QEICTL** register is clear.

QEI Velocity Counter (QEICOUNT)

QEI0 base: 0x4002.C000 QEI1 base: 0x4002.D000 Offset 0x018 Type RO, reset 0x0000.0000



The running total of encoder pulses during this velocity timer period.

Register 8: QEI Velocity (QEISPEED), offset 0x01C


This register contains the most recently measured velocity of the quadrature encoder. This value corresponds to the number of velocity pulses counted in the previous velocity timer period. This register does not update when the VELEN bit in the **QEICTL** register is clear.

QEI Velocity (QEISPEED)

QEI0 base: 0x4002.C000 QEI1 base: 0x4002.D000

Offset 0x01C

Type RO, reset 0x0000.0000



The measured speed of the quadrature encoder in pulses per period.


Register 9: QEI Interrupt Enable (QEIINTEN), offset 0x020

This register contains enables for each of the QEI module interrupts. An interrupt is asserted to the interrupt controller if the corresponding bit in this register is set.

QEI Interrupt Enable (QEIINTEN)

QEI0 base: 0x4002.C000 QEI1 base: 0x4002.D000 Offset 0x020

Type R/W, reset 0x0000.0000



Bit/Field	Name	Type	Reset	Description
31:4	reserved	RO	0x0000.000	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
3	INTERROR	R/W	0	Phase Error Interrupt Enable
				Value Description
				An interrupt is sent to the interrupt controller when the INTERROR bit in the QEIRIS register is set.
				O The INTERROR interrupt is suppressed and not sent to the interrupt controller.
2	INTDIR	R/W	0	Direction Change Interrupt Enable
				Value Description
				An interrupt is sent to the interrupt controller when the INTDIR bit in the QEIRIS register is set.
				O The INTDIR interrupt is suppressed and not sent to the interrupt controller.
1	INTTIMER	R/W	0	Timer Expires Interrupt Enable

Value Description

- An interrupt is sent to the interrupt controller when the INTTIMER bit in the QEIRIS register is set.
- 0 The ${\tt INTTIMER}$ interrupt is suppressed and not sent to the interrupt controller.

Bit/Field	Name	Туре	Reset	Description
0	INTINDEX	R/W	0	Index Pulse Detected Interrupt Enable
				Value Description
				An interrupt is sent to the interrupt controller when the INTINDEX bit in the QEIRIS register is set.
				O The INTINDEX interrupt is suppressed and not sent to the interrupt controller.


Register 10: QEI Raw Interrupt Status (QEIRIS), offset 0x024

This register provides the current set of interrupt sources that are asserted, regardless of whether they cause an interrupt to be asserted to the controller (configured through the **QEIINTEN** register). If a bit is set, the latched event has occurred; if a bit is clear, the event in question has not occurred.

QEI Raw Interrupt Status (QEIRIS)

QEI0 base: 0x4002.C000 QEI1 base: 0x4002.D000 Offset 0x024

Type RO, reset 0x0000.0000



Bit/Field	Name	Type	Reset	Description
31:4	reserved	RO	0x0000.000	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
3	INTERROR	RO	0	Phase Error Detected
				Value Description
				1 A phase error has been detected.
				0 An interrupt has not occurred.
				This bit is cleared by writing a 1 to the INTERROR bit in the QEIISC register.
2	INTDIR	RO	0	Direction Change Detected
				Value Description
				1 The rotation direction has changed
				0 An interrupt has not occurred.
				This bit is cleared by writing a 1 to the ${\tt INTDIR}$ bit in the ${\tt QEIISC}$ register.
1	INTTIMER	RO	0	Velocity Timer Expired
				Value Description

This bit is cleared by writing a 1 to the ${\tt INTTIMER}$ bit in the **QEIISC** register.

The velocity timer has expired.

An interrupt has not occurred.

1

0

Bit/Field	Name	Туре	Reset	Description
0	INTINDEX	RO	0	Index Pulse Asserted
				Value Description 1 The index pulse has occurred. 0 An interrupt has not occurred. This bit is cleared by writing a 1 to the INTINDEX bit in the QEIISC register.

Register 11: QEI Interrupt Status and Clear (QEIISC), offset 0x028

This register provides the current set of interrupt sources that are asserted to the controller. If a bit is set, the latched event has occurred and is enabled to generate an interrupt; if a bit is clear the event in question has not occurred or is not enabled to generate an interrupt. This register is R/W1C; writing a 1 to a bit position clears the bit and the corresponding interrupt reason.

QEI Interrupt Status and Clear (QEIISC)


Name

QEI0 base: 0x4002.C000 QEI1 base: 0x4002.D000

Offset 0x028

Bit/Field

Type R/W1C, reset 0x0000.0000



Reset

Type

31:4	reserved	RO	0x0000.000	Software should not rely on the value of a reserved bit. To provide compatibility with future products, the value of a reserved bit should be preserved across a read-modify-write operation.
3	INTERROR	R/W1C	0	Phase Error Interrupt

Description

Value Description

- The INTERROR bits in the QEIRIS register and the QEIINTEN registers are set, providing an interrupt to the interrupt controller.
- 0 No interrupt has occurred or the interrupt is masked.

This bit is cleared by writing a 1. Clearing this bit also clears the ${\tt INTERROR}$ bit in the ${\tt QEIRIS}$ register.

2	INTDIR	R/W1C	Ω	Direction Change Interrupt

Value Description

- 1 The INTDIR bits in the QEIRIS register and the QEIINTEN registers are set, providing an interrupt to the interrupt controller.
- No interrupt has occurred or the interrupt is masked.

This bit is cleared by writing a 1. Clearing this bit also clears the ${\tt INTDIR}$ bit in the ${\tt QEIRIS}$ register.

1 INTTIMER R/W1C 0 Velocity Timer Expired Interrupt

Value Description

- 1 The INTTIMER bits in the QEIRIS register and the QEIINTEN registers are set, providing an interrupt to the interrupt controller.
- 0 No interrupt has occurred or the interrupt is masked.

This bit is cleared by writing a 1. Clearing this bit also clears the INTTIMER bit in the **QEIRIS** register.


Bit/Field	Name	Туре	Reset	Description
0	INTINDEX	R/W1C	0	Index Pulse Interrupt
				Value Description
				The INTINDEX bits in the QEIRIS register and the QEIINTEN registers are set, providing an interrupt to the interrupt controller.
				0 No interrupt has occurred or the interrupt is masked.
				This bit is cleared by writing a 1. Clearing this bit also clears the INTINDEX bit in the QEIRIS register.

22 Pin Diagram

The LM4F232H5QC microcontroller pin diagram is shown below.

Each GPIO signal is identified by its GPIO port unless it defaults to an alternate function on reset. In this case, the GPIO port name is followed by the default alternate function. To see a complete list of possible functions for each pin, see Table 23-5 on page 1367.

Figure 22-1. 100-Pin LQFP Package Pin Diagram



23 Signal Tables

The following tables list the signals available for each pin. Signals are configured as GPIOs on reset, except for those noted below. Use the **GPIOAMSEL** register (see page 686) to select analog mode. For a GPIO pin to be used for an alternate digital function, the corresponding bit in the **GPIOAFSEL** register (see page 670) must be set. Further pin muxing options are provided through the PMCx bit field in the **GPIOPCTL** register (see page 688), which selects one of several available peripheral functions for that GPIO.

Important: All GPIO pins are configured as GPIOs by default with the exception of the pins shown in the table below. A Power-On-Reset (POR) or asserting RST puts the pins back to their default state.

GPIO Pin	Default State	GPIOAFSEL Bit	GPIOPCTL PMCx Bit Field
PA[1:0]	UART0	0	0x1
PA[5:2]	SSI0	0	0x1
PB[3:2]	I ² C0	0	0x1
PC[3:0]	JTAG/SWD	1	0x3

Table 23-1. GPIO Pins With Default Alternate Functions

Table 23-2 on page 1337 shows the pin-to-signal-name mapping, including functional characteristics of the signals. Each possible alternate analog and digital function is listed for each pin.

Table 23-3 on page 1348 lists the signals in alphabetical order by signal name. If it is possible for a signal to be on multiple pins, each possible pin assignment is listed. The "Pin Mux" column indicates the GPIO and the encoding needed in the PMCx bit field in the **GPIOPCTL** register.

Table 23-4 on page 1358 groups the signals by functionality, except for GPIOs. If it is possible for a signal to be on multiple pins, each possible pin assignment is listed.

Table 23-5 on page 1367 lists the GPIO pins and their analog and digital alternate functions. The AINx analog signals are not 5-V tolerant and go through an isolation circuit before reaching their circuitry. These signals are configured by clearing the corresponding DEN bit in the **GPIO Digital Enable** (**GPIODEN**) register and setting the corresponding AMSEL bit in the **GPIO Analog Mode Select** (**GPIOAMSEL**) register. Other analog signals are 5-V tolerant and are connected directly to their circuitry (C0-, C0+, C1-, C1+, C2-, C2+, USB0VBUS, USB0ID). These signals are configured by clearing the DEN bit in the **GPIO Digital Enable** (**GPIODEN**) register. The digital signals are enabled by setting the appropriate bit in the **GPIO Alternate Function Select** (**GPIOAFSEL**) and **GPIODEN** registers and configuring the PMCx bit field in the **GPIO Port Control** (**GPIOPCTL**) register to the numeric enoding shown in the table below. Table entries that are shaded gray are the default values for the corresponding GPIO pin.

Table 23-6 on page 1370 lists the signals based on number of possible pin assignments. This table can be used to plan how to configure the pins for a particular functionality. Application Note AN01274 Configuring Stellaris[®] Microcontrollers with Pin Multiplexing provides an overview of the pin muxing implementation, an explanation of how a system designer defines a pin configuration, and examples of the pin configuration process.

Note: All digital inputs are Schmitt triggered.

23.1 Signals by Pin Number

Table 23-2. Signals by Pin Number

Pin Number	Pin Name	Pin Type	Buffer Type ^a	Description
	PD0	I/O	TTL	GPIO port D bit 0.
	AIN15	I	Analog	Analog-to-digital converter input 15.
	I2C3SCL	I/O	OD	I ² C module 3 clock. Note that this signal has an active pull-up. The corresponding port pin should not be configured as open drain.
1	МОРWМб	0	TTL	Motion Control Module 0 PWM 6. This signal is controlled by Module 0 PWM Generator 3.
·	M1PWM0	0	TTL	Motion Control Module 1 PWM 0. This signal is controlled by Module 1 PWM Generator 0.
	SSI1Clk	I/O	TTL	SSI module 1 clock.
	SSI3Clk	I/O	TTL	SSI module 3 clock.
	WT2CCP0	I/O	TTL	32/64-Bit Wide Timer 2 Capture/Compare/PWM 0.
	PD1	I/O	TTL	GPIO port D bit 1.
	AIN14	I	Analog	Analog-to-digital converter input 14.
	I2C3SDA	I/O	OD	I ² C module 3 data.
2	морwм7	0	TTL	Motion Control Module 0 PWM 7. This signal is controlled by Module 0 PWM Generator 3.
2	M1PWM1	0	TTL	Motion Control Module 1 PWM 1. This signal is controlled by Module 1 PWM Generator 0.
	SSI1Fss	I/O	TTL	SSI module 1 frame signal.
	SSI3Fss	I/O	TTL	SSI module 3 frame signal.
	WT2CCP1	I/O	TTL	32/64-Bit Wide Timer 2 Capture/Compare/PWM 1.
	PD2	I/O	TTL	GPIO port D bit 2.
	AIN13	I	Analog	Analog-to-digital converter input 13.
	M0FAULT0	I	TTL	Motion Control Module 0 PWM Fault 0.
3	SSI1Rx	I	TTL	SSI module 1 receive.
Ŭ	SSI3Rx	I	TTL	SSI module 3 receive.
	USB0EPEN	0	TTL	Optionally used in Host mode to control an external power source to supply power to the USB bus.
	WT3CCP0	I/O	TTL	32/64-Bit Wide Timer 3 Capture/Compare/PWM 0.
	PD3	I/O	TTL	GPIO port D bit 3.
	AIN12	I	Analog	Analog-to-digital converter input 12.
	IDX0	I	TTL	QEI module 0 index.
4	SSI1Tx	0	TTL	SSI module 1 transmit.
•	SSI3Tx	0	TTL	SSI module 3 transmit.
	USB0PFLT	I	TTL	Optionally used in Host mode by an external power source to indicate an error state by that power source.
	WT3CCP1	I/O	TTL	32/64-Bit Wide Timer 3 Capture/Compare/PWM 1.
5	VDD	-	Power	Positive supply for I/O and some logic.
6	GND	-	Power	Ground reference for logic and I/O pins.

Table 23-2. Signals by Pin Number (continued)

Pin Number	Pin Name	Pin Type	Buffer Type ^a	Description
7	VDDA	-	Power	The positive supply for the analog circuits (ADC, Analog Comparators, etc.). These are separated from VDD to minimize the electrical noise contained on VDD from affecting the analog functions. VDDA pins must be supplied with a voltage that meets the specification in Table 24-5 on page 1378, regardless of system implementation.
8	VREFA+	-	Analog	A reference voltage used to specify the voltage at which the ADC converts to a maximum value. This pin is used in conjunction with $\tt VREFA-$ which specifies the minimum value. In other words, the voltage that is applied to $\tt VREFA+$ is the voltage with which an $\tt AINn$ signal is converted to 4095. The $\tt VREFA+$ voltage is limited to the range specified in Table 24-31 on page 1403 .
9	VREFA-	-	Analog	A reference voltage used to specify the input voltage at which the ADC converts to a minimum value. This pin is used in conjunction with $\mathtt{VREFA+}$ which specifies the maximum value. In other words, the voltage that is applied to $\mathtt{VREFA-}$ is the voltage with which an \mathtt{AINn} signal is converted to 0, while the voltage that is applied to $\mathtt{VREFA+}$ is the voltage with which an \mathtt{AINn} signal is converted to 4095. The $\mathtt{VREFA-}$ voltage is limited to the range specified in Table 24-31 on page 1403 .
10	GNDA	-	Power	The ground reference for the analog circuits (ADC, Analog Comparators, etc.). These are separated from GND to minimize the electrical noise contained on VDD from affecting the analog functions.
	PJ2	I/O	TTL	GPIO port J bit 2.
11 -	IDX0	I	TTL	QEI module 0 index.
''	T2CCP0	I/O	TTL	16/32-Bit Timer 2 Capture/Compare/PWM 0.
	U5Rx	I	TTL	UART module 5 receive.
12	PE3	I/O	TTL	GPIO port E bit 3.
12	AIN0	I	Analog	Analog-to-digital converter input 0.
13	PE2	I/O	TTL	GPIO port E bit 2.
15	AIN1	I	Analog	Analog-to-digital converter input 1.
	PE1	I/O	TTL	GPIO port E bit 1.
14	AIN2	I	Analog	Analog-to-digital converter input 2.
	U7Tx	0	TTL	UART module 7 transmit.
	PE0	I/O	TTL	GPIO port E bit 0.
15	AIN3	I	Analog	Analog-to-digital converter input 3.
	U7Rx	I	TTL	UART module 7 receive.
	РН0	I/O	TTL	GPIO port H bit 0.
	AIN16	I	Analog	Analog-to-digital converter input 16.
	M0FAULT0	I	TTL	Motion Control Module 0 PWM Fault 0.
16	м0РWМ0	0	TTL	Motion Control Module 0 PWM 0. This signal is controlled by Module 0 PWM Generator 0.
	SSI3Clk	I/O	TTL	SSI module 3 clock.
	WT2CCP0	I/O	TTL	32/64-Bit Wide Timer 2 Capture/Compare/PWM 0.

Table 23-2. Signals by Pin Number (continued)

Pin Number	Pin Name	Pin Type	Buffer Type ^a	Description
	PH1	I/O	TTL	GPIO port H bit 1.
	AIN17	I	Analog	Analog-to-digital converter input 17.
17	IDX0	I	TTL	QEI module 0 index.
17	M0FAULT1	1	TTL	Motion Control Module 0 PWM Fault 1.
''	M0PWM1	0	TTL	Motion Control Module 0 PWM 1. This signal is controlled by Module 0 PWM Generator 0.
	SSI3Fss	I/O	TTL	SSI module 3 frame signal.
	WT2CCP1	I/O	TTL	32/64-Bit Wide Timer 2 Capture/Compare/PWM 1.
	PH2	I/O	TTL	GPIO port H bit 2.
	AIN18	I	Analog	Analog-to-digital converter input 18.
	M0FAULT2	I	TTL	Motion Control Module 0 PWM Fault 2.
18	MOPWM2	0	TTL	Motion Control Module 0 PWM 2. This signal is controlled by Module 0 PWM Generator 1.
	SSI3Rx	ı	TTL	SSI module 3 receive.
	WT5CCP0	I/O	TTL	32/64-Bit Wide Timer 5 Capture/Compare/PWM 0.
	РН3	I/O	TTL	GPIO port H bit 3.
	AIN19	I	Analog	Analog-to-digital converter input 19.
	M0FAULT3	I	TTL	Motion Control Module 0 PWM Fault 3.
19	MOPWM3	0	TTL	Motion Control Module 0 PWM 3. This signal is controlled by Module 0 PWM Generator 1.
	SSI3Tx	0	TTL	SSI module 3 transmit.
	WT5CCP1	I/O	TTL	32/64-Bit Wide Timer 5 Capture/Compare/PWM 1.
20	VDD	-	Power	Positive supply for I/O and some logic.
21	GND	-	Power	Ground reference for logic and I/O pins.
	PC7	I/O	TTL	GPIO port C bit 7.
	C0-	I	Analog	Analog comparator 0 negative input.
22	U3Tx	0	TTL	UART module 3 transmit.
	USB0PFLT	I	TTL	Optionally used in Host mode by an external power source to indicate an error state by that power source.
	WT1CCP1	I/O	TTL	32/64-Bit Wide Timer 1 Capture/Compare/PWM 1.
	PC6	I/O	TTL	GPIO port C bit 6.
	C0+	I	Analog	Analog comparator 0 positive input.
	PhB1	ı	TTL	QEI module 1 phase B.
23	U3Rx	I	TTL	UART module 3 receive.
	USB0EPEN	0	TTL	Optionally used in Host mode to control an external power source to supply power to the USB bus.
	WT1CCP0	I/O	TTL	32/64-Bit Wide Timer 1 Capture/Compare/PWM 0.

Table 23-2. Signals by Pin Number (continued)

Pin Number	Pin Name	Pin Type	Buffer Type ^a	Description
	PC5	I/O	TTL	GPIO port C bit 5.
	C1+	I	Analog	Analog comparator 1 positive input.
	MOPWM7	0	TTL	Motion Control Module 0 PWM 7. This signal is controlled by Module 0 PWM Generator 3.
24	PhA1	I	TTL	QEI module 1 phase A.
	U1CTS	ı	TTL	UART module 1 Clear To Send modem flow control input signal.
	U1Tx	0	TTL	UART module 1 transmit.
	U4Tx	0	TTL	UART module 4 transmit.
	WT0CCP1	I/O	TTL	32/64-Bit Wide Timer 0 Capture/Compare/PWM 1.
	PC4	I/O	TTL	GPIO port C bit 4.
	C1-	I	Analog	Analog comparator 1 negative input.
	IDX1	I	TTL	QEI module 1 index.
25	МОРWМб	0	TTL	Motion Control Module 0 PWM 6. This signal is controlled by Module 0 PWM Generator 3.
	U1RTS	0	TTL	UART module 1 Request to Send modem flow control output line.
	U1Rx	I	TTL	UART module 1 receive.
	U4Rx	I	TTL	UART module 4 receive.
	WT0CCP0	I/O	TTL	32/64-Bit Wide Timer 0 Capture/Compare/PWM 0.
	PA0	I/O	TTL	GPIO port A bit 0.
26	CAN1Rx	I	TTL	CAN module 1 receive.
	U0Rx	I	TTL	UART module 0 receive.
	PA1	I/O	TTL	GPIO port A bit 1.
27	CAN1Tx	0	TTL	CAN module 1 transmit.
	U0Tx	0	TTL	UART module 0 transmit.
20	PA2	I/O	TTL	GPIO port A bit 2.
28 —	SSIOClk	I/O	TTL	SSI module 0 clock
20	PA3	I/O	TTL	GPIO port A bit 3.
29	SSI0Fss	I/O	TTL	SSI module 0 frame signal
20	PA4	I/O	TTL	GPIO port A bit 4.
30	SSI0Rx	I	TTL	SSI module 0 receive
24	PA5	I/O	TTL	GPIO port A bit 5.
31 —	SSI0Tx	0	TTL	SSI module 0 transmit
32	VDD	-	Power	Positive supply for I/O and some logic.
33	GND	-	Power	Ground reference for logic and I/O pins.
	PA6	I/O	TTL	GPIO port A bit 6.
34	I2C1SCL	I/O	OD	I ² C module 1 clock. Note that this signal has an active pull-up. The corresponding port pin should not be configured as open drain.
	M1PWM2	0	TTL	Motion Control Module 1 PWM 2. This signal is controlled by Module 1 PWM Generator 1.
	PA7	I/O	TTL	GPIO port A bit 7.
35	I2C1SDA	I/O	OD	I ² C module 1 data.
	M1PWM3	0	TTL	Motion Control Module 1 PWM 3. This signal is controlled by Module 1 PWM Generator 1.

Table 23-2. Signals by Pin Number (continued)

Pin Number	Pin Name	Pin Type	Buffer Type ^a	Description
	PF6	I/O	TTL	GPIO port F bit 6.
36	I2C2SCL	I/O	OD	I ² C module 2 clock. Note that this signal has an active pull-up. The corresponding port pin should not be configured as open drain.
	T3CCP0	I/O	TTL	16/32-Bit Timer 3 Capture/Compare/PWM 0.
	PF5	I/O	TTL	GPIO port F bit 5.
	M0FAULT3	I	TTL	Motion Control Module 0 PWM Fault 3.
37	T2CCP1	I/O	TTL	16/32-Bit Timer 2 Capture/Compare/PWM 1.
	USB0PFLT	I	TTL	Optionally used in Host mode by an external power source to indicate an error state by that power source.
38	VDDC	-	Power	Positive supply for most of the logic function, including the processor core and most peripherals. The voltage on this pin is 1.2 V and is supplied by the on-chip LDO. The VDDC pins should only be connected to each other and an external capacitor as specified in Table 24-12 on page 1390.
	PF4	I/O	TTL	GPIO port F bit 4.
	IDX0	1	TTL	QEI module 0 index.
	M0FAULT2	I	TTL	Motion Control Module 0 PWM Fault 2.
	M1FAULT0	I I	TTL	Motion Control Module 1 PWM Fault 0.
39	T2CCP0	I/O	TTL	16/32-Bit Timer 2 Capture/Compare/PWM 0.
	TRD3	0	TTL	Trace data 3.
	U1DTR	0	TTL	UART module 1 Data Terminal Ready modem status input signal
	USB0EPEN	0	TTL	Optionally used in Host mode to control an external power source to supply power to the USB bus.
	PF0	I/O	TTL	GPIO port F bit 0.
	C0o	0	TTL	Analog comparator 0 output.
	CAN0Rx	I	TTL	CAN module 0 receive.
	M1PWM4	0	TTL	Motion Control Module 1 PWM 4. This signal is controlled by Module 1 PWM Generator 2.
40	NMI	I	TTL	Non-maskable interrupt.
	PhA0	I	TTL	QEI module 0 phase A.
	SSI1Rx	I	TTL	SSI module 1 receive.
	T0CCP0	I/O	TTL	16/32-Bit Timer 0 Capture/Compare/PWM 0.
	TRD2	0	TTL	Trace data 2.
	U1RTS	0	TTL	UART module 1 Request to Send modem flow control output line
	PF1	I/O	TTL	GPIO port F bit 1.
	Clo	0	TTL	Analog comparator 1 output.
	M1PWM5	0	TTL	Motion Control Module 1 PWM 5. This signal is controlled by Module 1 PWM Generator 2.
41	PhB0	I	TTL	QEI module 0 phase B.
	SSI1Tx	0	TTL	SSI module 1 transmit.
	T0CCP1	I/O	TTL	16/32-Bit Timer 0 Capture/Compare/PWM 1.
	TRD1	0	TTL	Trace data 1.
	U1CTS	1	TTL	UART module 1 Clear To Send modem flow control input signal.

Table 23-2. Signals by Pin Number (continued)

Pin Number	Pin Name	Pin Type	Buffer Type ^a	Description
	PF2	I/O	TTL	GPIO port F bit 2.
	C2o	0	TTL	Analog comparator 2 output.
	M0FAULT0	I	TTL	Motion Control Module 0 PWM Fault 0.
42	M1PWM6	0	TTL	Motion Control Module 1 PWM 6. This signal is controlled by Module 1 PWM Generator 3.
	SSI1Clk	I/O	TTL	SSI module 1 clock.
	T1CCP0	I/O	TTL	16/32-Bit Timer 1 Capture/Compare/PWM 0.
	TRD0	0	TTL	Trace data 0.
	U1DCD	ı	TTL	UART module 1 Data Carrier Detect modem status input signal.
	PF3	I/O	TTL	GPIO port F bit 3.
	CANOTX	0	TTL	CAN module 0 transmit.
	M0FAULT1	ı	TTL	Motion Control Module 0 PWM Fault 1.
43	M1PWM7	0	TTL	Motion Control Module 1 PWM 7. This signal is controlled by Module 1 PWM Generator 3.
	SSI1Fss	I/O	TTL	SSI module 1 frame signal.
	T1CCP1	I/O	TTL	16/32-Bit Timer 1 Capture/Compare/PWM 1.
	TRCLK	0	TTL	Trace clock.
	U1DSR	ı	TTL	UART module 1 Data Set Ready modem output control line.
44	VDD	-	Power	Positive supply for I/O and some logic.
45	GND	-	Power	Ground reference for logic and I/O pins.
	PK3	I/O	TTL	GPIO port K bit 3.
46	M1FAULT3	I	TTL	Motion Control Module 1 PWM Fault 3.
	SSI3Tx	0	TTL	SSI module 3 transmit.
	PK2	I/O	TTL	GPIO port K bit 2.
47	M1FAULT2	I	TTL	Motion Control Module 1 PWM Fault 2.
	SSI3Rx	I	TTL	SSI module 3 receive.
	PK1	I/O	TTL	GPIO port K bit 1.
48	M1FAULT1	I	TTL	Motion Control Module 1 PWM Fault 1.
	SSI3Fss	I/O	TTL	SSI module 3 frame signal.
	PK0	I/O	TTL	GPIO port K bit 0.
49	M1FAULT0	ı	TTL	Motion Control Module 1 PWM Fault 0.
	SSI3Clk	I/O	TTL	SSI module 3 clock.
50	WAKE	I	TTL	An external input that brings the processor out of Hibernate mode when asserted.
51	HIB	0	TTL	An output that indicates the processor is in Hibernate mode.
52	XOSC0	I	Analog	Hibernation module oscillator crystal input or an external clock reference input. Note that this is either a 32.768-kHz crystal or a 32.768-kHz oscillator for the Hibernation module RTC.
53	GNDX	-	Power	GND for the Hibernation oscillator. When using a crystal clock source, this pin should only be connected to the crystal load capacitors to improve oscillator immunity to system noise. When using an external oscillator, this pin should be connected to GND.
54	XOSC1	0	Analog	Hibernation module oscillator crystal output. Leave unconnected when using a single-ended clock source.

Table 23-2. Signals by Pin Number (continued)

Pin Number	Pin Name	Pin Type	Buffer Type ^a	Description
55	VBAT	-	Power	Power source for the Hibernation module. It is normally connected to the positive terminal of a battery and serves as the battery backup/Hibernation module power-source supply.
56	VDD	-	Power	Positive supply for I/O and some logic.
57	GND	-	Power	Ground reference for logic and I/O pins.
	PF7	I/O	TTL	GPIO port F bit 7.
58	I2C2SDA	I/O	OD	I ² C module 2 data.
56	M1FAULT0	I	TTL	Motion Control Module 1 PWM Fault 0.
	T3CCP1	I/O	TTL	16/32-Bit Timer 3 Capture/Compare/PWM 1.
	PG3	I/O	TTL	GPIO port G bit 3.
	I2C4SDA	I/O	OD	I ² C module 4 data.
Ī	M0FAULT2	I	TTL	Motion Control Module 0 PWM Fault 2.
59	M1PWM1	0	TTL	Motion Control Module 1 PWM 1. This signal is controlled by Module 1 PWM Generator 0.
	PhA1	I	TTL	QEI module 1 phase A.
	T5CCP1	I/O	TTL	16/32-Bit Timer 5 Capture/Compare/PWM 1.
	PG2	I/O	TTL	GPIO port G bit 2.
	I2C4SCL	I/O	OD	I ² C module 4 clock. Note that this signal has an active pull-up. The corresponding port pin should not be configured as open drain.
60	M0FAULT1	I	TTL	Motion Control Module 0 PWM Fault 1.
	M1PWM0	0	TTL	Motion Control Module 1 PWM 0. This signal is controlled by Module 1 PWM Generator 0.
	T5CCP0	I/O	TTL	16/32-Bit Timer 5 Capture/Compare/PWM 0.
	PG1	I/O	TTL	GPIO port G bit 1.
	I2C3SDA	I/O	OD	I ² C module 3 data.
61	M1FAULT2	I	TTL	Motion Control Module 1 PWM Fault 2.
	PhB1	I	TTL	QEI module 1 phase B.
Ī	T4CCP1	I/O	TTL	16/32-Bit Timer 4 Capture/Compare/PWM 1.
	PG0	I/O	TTL	GPIO port G bit 0.
	I2C3SCL	I/O	OD	I ² C module 3 clock. Note that this signal has an active pull-up. The corresponding port pin should not be configured as open drain.
62	M1FAULT1	I	TTL	Motion Control Module 1 PWM Fault 1.
	PhA1	I	TTL	QEI module 1 phase A.
	T4CCP0	I/O	TTL	16/32-Bit Timer 4 Capture/Compare/PWM 0.
63	RST	I	TTL	System reset input.
64	GND	-	Power	Ground reference for logic and I/O pins.
65	osc0	I	Analog	Main oscillator crystal input or an external clock reference input.
66	OSC1	0	Analog	Main oscillator crystal output. Leave unconnected when using a single-ended clock source.
67	VDD	-	Power	Positive supply for I/O and some logic.

Table 23-2. Signals by Pin Number (continued)

Pin Number	Pin Name	Pin Type	Buffer Type ^a	Description
	PJ0	I/O	TTL	GPIO port J bit 0. This pin is not 5-V tolerant.
	T1CCP0	I/O	TTL	16/32-Bit Timer 1 Capture/Compare/PWM 0.
68	U4Rx	I	TTL	UART module 4 receive.
	USB0DM	I/O	Analog	Bidirectional differential data pin (D- per USB specification) for USB0.
	PJ1	I/O	TTL	GPIO port J bit 1. This pin is not 5-V tolerant.
	T1CCP1	I/O	TTL	16/32-Bit Timer 1 Capture/Compare/PWM 1.
69	U4Tx	0	TTL	UART module 4 transmit.
	USB0DP	I/O	Analog	Bidirectional differential data pin (D+ per USB specification) for USB0.
	PB0	I/O	TTL	GPIO port B bit 0. This pin is not 5-V tolerant.
	T2CCP0	I/O	TTL	16/32-Bit Timer 2 Capture/Compare/PWM 0.
70	U1Rx	I	TTL	UART module 1 receive.
70	USB0ID	I	Analog	This signal senses the state of the USB ID signal. The USB PHY enables an integrated pull-up, and an external element (USB connector) indicates the initial state of the USB controller (pulled down is the A side of the cable and pulled up is the B side).
	PB1	I/O	TTL	GPIO port B bit 1. This pin is not 5-V tolerant.
71	T2CCP1	I/O	TTL	16/32-Bit Timer 2 Capture/Compare/PWM 1.
	UlTx	0	TTL	UART module 1 transmit.
	USB0VBUS	I/O	Analog	This signal is used during the session request protocol. This signal allows the USB PHY to both sense the voltage level of VBUS, and pull up VBUS momentarily during VBUS pulsing.
	PB2	I/O	TTL	GPIO port B bit 2.
72	I2C0SCL	I/O	OD	I ² C module 0 clock. Note that this signal has an active pull-up. The corresponding port pin should not be configured as open drain.
	T3CCP0	I/O	TTL	16/32-Bit Timer 3 Capture/Compare/PWM 0.
	PB3	I/O	TTL	GPIO port B bit 3.
73	I2C0SDA	I/O	OD	I ² C module 0 data.
	T3CCP1	I/O	TTL	16/32-Bit Timer 3 Capture/Compare/PWM 1.
	PG4	I/O	TTL	GPIO port G bit 4.
	I2C1SCL	I/O	OD	I ² C module 1 clock. Note that this signal has an active pull-up. The corresponding port pin should not be configured as open drain.
	M0PWM4	0	TTL	Motion Control Module 0 PWM 4. This signal is controlled by Module 0 PWM Generator 2.
74	M1PWM2	0	TTL	Motion Control Module 1 PWM 2. This signal is controlled by Module 1 PWM Generator 1.
	PhB1	I	TTL	QEI module 1 phase B.
	U2Rx	I	TTL	UART module 2 receive.
	USB0EPEN	0	TTL	Optionally used in Host mode to control an external power source to supply power to the USB bus.
	WT0CCP0	I/O	TTL	32/64-Bit Wide Timer 0 Capture/Compare/PWM 0.

Table 23-2. Signals by Pin Number (continued)

Pin Number	Pin Name	Pin Type	Buffer Type ^a	Description
	PG5	I/O	TTL	GPIO port G bit 5.
	I2C1SDA	I/O	OD	I ² C module 1 data.
	IDX1	I	TTL	QEI module 1 index.
	M0PWM5	0	TTL	Motion Control Module 0 PWM 5. This signal is controlled by Module 0 PWM Generator 2.
75	M1PWM3	0	TTL	Motion Control Module 1 PWM 3. This signal is controlled by Module 1 PWM Generator 1.
	U2Tx	0	TTL	UART module 2 transmit.
	USB0PFLT	I	TTL	Optionally used in Host mode by an external power source to indicate an error state by that power source.
	WT0CCP1	I/O	TTL	32/64-Bit Wide Timer 0 Capture/Compare/PWM 1.
	PH7	I/O	TTL	GPIO port H bit 7.
76	MOPWM7	0	TTL	Motion Control Module 0 PWM 7. This signal is controlled by Module 0 PWM Generator 3.
	SSI2Tx	0	TTL	SSI module 2 transmit.
	WT4CCP1	I/O	TTL	32/64-Bit Wide Timer 4 Capture/Compare/PWM 1.
	РН6	I/O	TTL	GPIO port H bit 6.
77	морwмб	0	TTL	Motion Control Module 0 PWM 6. This signal is controlled by Module 0 PWM Generator 3.
	SSI2Rx	I	TTL	SSI module 2 receive.
	WT4CCP0	I/O	TTL	32/64-Bit Wide Timer 4 Capture/Compare/PWM 0.
	PH5	I/O	TTL	GPIO port H bit 5.
[м0РWМ5	0	TTL	Motion Control Module 0 PWM 5. This signal is controlled by Module 0 PWM Generator 2.
78	PhB0	I	TTL	QEI module 0 phase B.
	SSI2Fss	I/O	TTL	SSI module 2 frame signal.
	WT3CCP1	I/O	TTL	32/64-Bit Wide Timer 3 Capture/Compare/PWM 1.
	PH4	I/O	TTL	GPIO port H bit 4.
	м0рwм4	0	TTL	Motion Control Module 0 PWM 4. This signal is controlled by Module 0 PWM Generator 2.
79	PhA0	I	TTL	QEI module 0 phase A.
	SSI2Clk	I/O	TTL	SSI module 2 clock.
	WT3CCP0	I/O	TTL	32/64-Bit Wide Timer 3 Capture/Compare/PWM 0.
80	VDD	-	Power	Positive supply for I/O and some logic.
81	GND	-	Power	Ground reference for logic and I/O pins.
	PC3	I/O	TTL	GPIO port C bit 3.
82	SWO	0	TTL	JTAG TDO and SWO.
	T5CCP1	I/O	TTL	16/32-Bit Timer 5 Capture/Compare/PWM 1.
	TDO	0	TTL	JTAG TDO and SWO.
	PC2	I/O	TTL	GPIO port C bit 2.
83	T5CCP0	I/O	TTL	16/32-Bit Timer 5 Capture/Compare/PWM 0.
	TDI	I	TTL	JTAG TDI.

Table 23-2. Signals by Pin Number (continued)

Pin Number	Pin Name	Pin Type	Buffer Type ^a	Description	
	PC1	I/O	TTL	GPIO port C bit 1.	
84	SWDIO	I/O	TTL	JTAG TMS and SWDIO.	
04	T4CCP1	I/O	TTL	16/32-Bit Timer 4 Capture/Compare/PWM 1.	
	TMS	I	TTL	JTAG TMS and SWDIO.	
	PC0	I/O	TTL	GPIO port C bit 0.	
95	SWCLK	ı	TTL	JTAG/SWD CLK.	
65	74CCP0		TTL	16/32-Bit Timer 4 Capture/Compare/PWM 0.	
	TCK	I	TTL	JTAG/SWD CLK.	
86	VDDC	-	Power	Positive supply for most of the logic function, including the processor core and most peripherals. The voltage on this pin is 1.2 V and is supplied by the on-chip LDO. The VDDC pins should only be connected to each other and an external capacitor as specified in Table 24-12 on page 1390.	
	PG6	I/O	TTL	GPIO port G bit 6.	
	C2+	I	Analog	Analog comparator 2 positive input.	
87	I2C5SCL	I/O	OD	$\rm I^2C$ module 5 clock. Note that this signal has an active pull-up. The corresponding port pin should not be configured as open drain.	
	МОРWМб	0	TTL	Motion Control Module 0 PWM 6. This signal is controlled by Module 0 PWM Generator 3.	
	WT1CCP0	I/O	TTL	32/64-Bit Wide Timer 1 Capture/Compare/PWM 0.	
	PG7	I/O	TTL	GPIO port G bit 7.	
	C2-	I	Analog	Analog comparator 2 negative input.	
	I2C5SDA	I/O	OD	I ² C module 5 data.	
88	IDX1	I	TTL	QEI module 1 index.	
	MOPWM7	0	TTL	Motion Control Module 0 PWM 7. This signal is controlled by Module 0 PWM Generator 3.	
	WT1CCP1	I/O	TTL	32/64-Bit Wide Timer 1 Capture/Compare/PWM 1.	
	PE6	I/O	TTL	GPIO port E bit 6.	
89	AIN21	I	Analog	Analog-to-digital converter input 21.	
	CAN1Rx	I	TTL	CAN module 1 receive.	
	PE7	I/O	TTL	GPIO port E bit 7.	
90	AIN20	I	Analog	Analog-to-digital converter input 20.	
90	CAN1Tx	0	TTL	CAN module 1 transmit.	
	U1RI	I	TTL	UART module 1 Ring Indicator modem status input signal.	
	PB5	I/O	TTL	GPIO port B bit 5.	
	AIN11	I	Analog	Analog-to-digital converter input 11.	
	CAN0Tx	0	TTL	CAN module 0 transmit.	
91	морwм3	0	TTL	Motion Control Module 0 PWM 3. This signal is controlled by Module 0 PWM Generator 1.	
	SSI2Fss	I/O	TTL	SSI module 2 frame signal.	
	T1CCP1	I/O	TTL	16/32-Bit Timer 1 Capture/Compare/PWM 1.	

Table 23-2. Signals by Pin Number (continued)

Pin Number	Pin Name	Pin Type	Buffer Type ^a	Description	
	PB4	I/O	TTL	GPIO port B bit 4.	
	AIN10	I	Analog	Analog-to-digital converter input 10.	
	CAN0Rx	I	TTL	CAN module 0 receive.	
92	MOPWM2	0	TTL	Motion Control Module 0 PWM 2. This signal is controlled by Module 0 PWM Generator 1.	
-	SSI2Clk	I/O	TTL	SSI module 2 clock.	
Ī	T1CCP0	I/O	TTL	16/32-Bit Timer 1 Capture/Compare/PWM 0.	
93	VDD	-	Power	Positive supply for I/O and some logic.	
94	GND	-	Power	Ground reference for logic and I/O pins.	
	PE4	I/O	TTL	GPIO port E bit 4.	
-	AIN9	I	Analog	Analog-to-digital converter input 9.	
	CAN0Rx	1	TTL	CAN module 0 receive.	
95	I2C2SCL	I/O	OD	I ² C module 2 clock. Note that this signal has an active pull-up. The corresponding port pin should not be configured as open drain.	
	MOPWM4	0	TTL	Motion Control Module 0 PWM 4. This signal is controlled by Module 0 PWM Generator 2.	
-	M1PWM2	0	TTL	Motion Control Module 1 PWM 2. This signal is controlled by Module 1 PWM Generator 1.	
	U5Rx	I	TTL	UART module 5 receive.	
	PE5	I/O	TTL	GPIO port E bit 5.	
	AIN8	I	Analog	Analog-to-digital converter input 8.	
	CAN0Tx	0	TTL	CAN module 0 transmit.	
	I2C2SDA	I/O	OD	I ² C module 2 data.	
96	M0PWM5	0	TTL	Motion Control Module 0 PWM 5. This signal is controlled by Module 0 PWM Generator 2.	
-	M1PWM3	0	TTL	Motion Control Module 1 PWM 3. This signal is controlled by Module 1 PWM Generator 1.	
-	U5Tx	0	TTL	UART module 5 transmit.	
	PD4	I/O	TTL	GPIO port D bit 4.	
07	AIN7	I	Analog	Analog-to-digital converter input 7.	
97	U6Rx	1	TTL	UART module 6 receive.	
-	WT4CCP0	I/O	TTL	32/64-Bit Wide Timer 4 Capture/Compare/PWM 0.	
	PD5	I/O	TTL	GPIO port D bit 5.	
00	AIN6	I	Analog	Analog-to-digital converter input 6.	
98	U6Tx	0	TTL	UART module 6 transmit.	
	WT4CCP1	I/O	TTL	32/64-Bit Wide Timer 4 Capture/Compare/PWM 1.	
	PD6	I/O	TTL	GPIO port D bit 6.	
	AIN5	1	Analog	Analog-to-digital converter input 5.	
00	M0FAULT0	1	TTL	Motion Control Module 0 PWM Fault 0.	
99	PhA0	I	TTL	QEI module 0 phase A.	
	U2Rx	1	TTL	UART module 2 receive.	
	WT5CCP0	I/O	TTL	32/64-Bit Wide Timer 5 Capture/Compare/PWM 0.	

Table 23-2. Signals by Pin Number (continued)

Pin Number	Pin Name	Pin Type	Buffer Type ^a	Description
	PD7	I/O	TTL	GPIO port D bit 7.
	AIN4	I	Analog	Analog-to-digital converter input 4.
	M0FAULT1	I	TTL	Motion Control Module 0 PWM Fault 1.
100	NMI	I	TTL	Non-maskable interrupt.
	PhB0	I	TTL	QEI module 0 phase B.
	U2Tx	0	TTL	UART module 2 transmit.
	WT5CCP1	I/O	TTL	32/64-Bit Wide Timer 5 Capture/Compare/PWM 1.

a. The TTL designation indicates the pin has TTL-compatible voltage levels.

23.2 Signals by Signal Name

Table 23-3. Signals by Signal Name

Pin Name	Pin Number	Pin Mux / Pin Assignment	Pin Type	Buffer Type ^a	Description
AIN0	12	PE3	I	Analog	Analog-to-digital converter input 0.
AIN1	13	PE2	I	Analog	Analog-to-digital converter input 1.
AIN2	14	PE1	ļ	Analog	Analog-to-digital converter input 2.
AIN3	15	PE0	I	Analog	Analog-to-digital converter input 3.
AIN4	100	PD7	ļ	Analog	Analog-to-digital converter input 4.
AIN5	99	PD6	ļ	Analog	Analog-to-digital converter input 5.
AIN6	98	PD5	ļ	Analog	Analog-to-digital converter input 6.
AIN7	97	PD4	ļ	Analog	Analog-to-digital converter input 7.
AIN8	96	PE5	ļ	Analog	Analog-to-digital converter input 8.
AIN9	95	PE4	I	Analog	Analog-to-digital converter input 9.
AIN10	92	PB4	I	Analog	Analog-to-digital converter input 10.
AIN11	91	PB5	ļ	Analog	Analog-to-digital converter input 11.
AIN12	4	PD3	ļ	Analog	Analog-to-digital converter input 12.
AIN13	3	PD2	I	Analog	Analog-to-digital converter input 13.
AIN14	2	PD1	ļ	Analog	Analog-to-digital converter input 14.
AIN15	1	PD0	I	Analog	Analog-to-digital converter input 15.
AIN16	16	PH0	ļ	Analog	Analog-to-digital converter input 16.
AIN17	17	PH1	I	Analog	Analog-to-digital converter input 17.
AIN18	18	PH2	I	Analog	Analog-to-digital converter input 18.
AIN19	19	PH3	I	Analog	Analog-to-digital converter input 19.
AIN20	90	PE7	I	Analog	Analog-to-digital converter input 20.
AIN21	89	PE6	I	Analog	Analog-to-digital converter input 21.
C0+	23	PC6	I	Analog	Analog comparator 0 positive input.
C0-	22	PC7	I	Analog	Analog comparator 0 negative input.
C0o	40	PF0 (9)	0	TTL	Analog comparator 0 output.
C1+	24	PC5	ı	Analog	Analog comparator 1 positive input.
C1-	25	PC4	I	Analog	Analog comparator 1 negative input.
Clo	41	PF1 (9)	0	TTL	Analog comparator 1 output.

Table 23-3. Signals by Signal Name (continued)

Pin Name	Pin Number	Pin Mux / Pin Assignment	Pin Type	Buffer Type ^a	Description
C2+	87	PG6	I	Analog	Analog comparator 2 positive input.
C2-	88	PG7	I	Analog	Analog comparator 2 negative input.
C20	42	PF2 (9)	0	TTL	Analog comparator 2 output.
CAN0Rx	40 92 95	PF0 (3) PB4 (8) PE4 (8)	I	TTL	CAN module 0 receive.
CAN0Tx	43 91 96	PF3 (3) PB5 (8) PE5 (8)	0	TTL	CAN module 0 transmit.
CAN1Rx	26 89	PA0 (8) PE6 (8)	I	TTL	CAN module 1 receive.
CAN1Tx	27 90	PA1 (8) PE7 (8)	0	TTL	CAN module 1 transmit.
GND	6 21 33 45 57 64 81 94	fixed	-	Power	Ground reference for logic and I/O pins.
GNDA	10	fixed	-	Power	The ground reference for the analog circuits (ADC, Analog Comparators, etc.). These are separated from GND to minimize the electrical noise contained on VDD from affecting the analog functions.
GNDX	53	fixed	-	Power	GND for the Hibernation oscillator. When using a crystal clock source, this pin should only be connected to the crystal load capacitors to improve oscillator immunity to system noise. When using an external oscillator, this pin should be connected to GND.
HIB	51	fixed	0	TTL	An output that indicates the processor is in Hibernate mode.
I2C0SCL	72	PB2 (3)	I/O	OD	I ² C module 0 clock. Note that this signal has an active pull-up. The corresponding port pin should not be configured as open drain.
I2C0SDA	73	PB3 (3)	I/O	OD	I ² C module 0 data.
I2C1SCL	34 74	PA6 (3) PG4 (3)	I/O	OD	I ² C module 1 clock. Note that this signal has an active pull-up. The corresponding port pin should not be configured as open drain.
I2C1SDA	35 75	PA7 (3) PG5 (3)	I/O	OD	I ² C module 1 data.
I2C2SCL	36 95	PF6 (3) PE4 (3)	I/O	OD	I ² C module 2 clock. Note that this signal has an active pull-up. The corresponding port pin should not be configured as open drain.
I2C2SDA	58 96	PF7 (3) PE5 (3)	I/O	OD	I ² C module 2 data.
I2C3SCL	1 62	PD0 (3) PG0 (3)	I/O	OD	I ² C module 3 clock. Note that this signal has an active pull-up. The corresponding port pin should not be configured as open drain.

Table 23-3. Signals by Signal Name (continued)

Pin Name	Pin Number	Pin Mux / Pin Assignment	Pin Type	Buffer Type ^a	Description
I2C3SDA	2 61	PD1 (3) PG1 (3)	I/O	OD	I ² C module 3 data.
I2C4SCL	60	PG2 (3)	I/O	OD	I ² C module 4 clock. Note that this signal has an active pull-up. The corresponding port pin should not be configured as open drain.
I2C4SDA	59	PG3 (3)	I/O	OD	I ² C module 4 data.
I2C5SCL	87	PG6 (3)	I/O	OD	I ² C module 5 clock. Note that this signal has an active pull-up. The corresponding port pin should not be configured as open drain.
I2C5SDA	88	PG7 (3)	I/O	OD	I ² C module 5 data.
IDX0	4 11 17 39	PD3 (6) PJ2 (5) PH1 (5) PF4 (6)	I	TTL	QEI module 0 index.
IDX1	25 75 88	PC4 (6) PG5 (6) PG7 (5)	I	TTL	QEI module 1 index.
M0FAULT0	3 16 42 99	PD2 (4) PH0 (6) PF2 (4) PD6 (4)	I	TTL	Motion Control Module 0 PWM Fault 0.
M0FAULT1	17 43 60 100	PH1 (6) PF3 (4) PG2 (4) PD7 (4)	I	TTL	Motion Control Module 0 PWM Fault 1.
M0FAULT2	18 39 59	PH2 (6) PF4 (4) PG3 (4)	I	TTL	Motion Control Module 0 PWM Fault 2.
M0FAULT3	19 37	PH3 (6) PF5 (4)	I	TTL	Motion Control Module 0 PWM Fault 3.
MOPWMO	16	PH0 (4)	0	TTL	Motion Control Module 0 PWM 0. This signal is controlled by Module 0 PWM Generator 0.
MOPWM1	17	PH1 (4)	0	TTL	Motion Control Module 0 PWM 1. This signal is controlled by Module 0 PWM Generator 0.
MOPWM2	18 92	PH2 (4) PB4 (4)	0	TTL	Motion Control Module 0 PWM 2. This signal is controlled by Module 0 PWM Generator 1.
MOPWM3	19 91	PH3 (4) PB5 (4)	0	TTL	Motion Control Module 0 PWM 3. This signal is controlled by Module 0 PWM Generator 1.
M0PWM4	74 79 95	PG4 (4) PH4 (4) PE4 (4)	0	TTL	Motion Control Module 0 PWM 4. This signal is controlled by Module 0 PWM Generator 2.
M0PWM5	75 78 96	PG5 (4) PH5 (4) PE5 (4)	0	TTL	Motion Control Module 0 PWM 5. This signal is controlled by Module 0 PWM Generator 2.
M0PWM6	1 25 77 87	PD0 (4) PC4 (4) PH6 (4) PG6 (4)	0	TTL	Motion Control Module 0 PWM 6. This signal is controlled by Module 0 PWM Generator 3.

Table 23-3. Signals by Signal Name (continued)

Pin Name	Pin Number	Pin Mux / Pin Assignment	Pin Type	Buffer Type ^a	Description
МОРWМ7	2 24 76 88	PD1 (4) PC5 (4) PH7 (4) PG7 (4)	0	TTL	Motion Control Module 0 PWM 7. This signal is controlled by Module 0 PWM Generator 3.
M1FAULT0	39 49 58	PF4 (5) PK0 (6) PF7 (5)	I	TTL	Motion Control Module 1 PWM Fault 0.
M1FAULT1	48 62	PK1 (6) PG0 (5)	I	TTL	Motion Control Module 1 PWM Fault 1.
M1FAULT2	47 61	PK2 (6) PG1 (5)	I	TTL	Motion Control Module 1 PWM Fault 2.
M1FAULT3	46	PK3 (6)	I	TTL	Motion Control Module 1 PWM Fault 3.
M1PWM0	1 60	PD0 (5) PG2 (5)	0	TTL	Motion Control Module 1 PWM 0. This signal is controlled by Module 1 PWM Generator 0.
M1PWM1	2 59	PD1 (5) PG3 (5)	0	TTL	Motion Control Module 1 PWM 1. This signal is controlled by Module 1 PWM Generator 0.
M1PWM2	34 74 95	PA6 (5) PG4 (5) PE4 (5)	0	TTL	Motion Control Module 1 PWM 2. This signal is controlled by Module 1 PWM Generator 1.
M1PWM3	35 75 96	PA7 (5) PG5 (5) PE5 (5)	0	TTL	Motion Control Module 1 PWM 3. This signal is controlled by Module 1 PWM Generator 1.
M1PWM4	40	PF0 (5)	0	TTL	Motion Control Module 1 PWM 4. This signal is controlled by Module 1 PWM Generator 2.
M1PWM5	41	PF1 (5)	0	TTL	Motion Control Module 1 PWM 5. This signal is controlled by Module 1 PWM Generator 2.
M1PWM6	42	PF2 (5)	0	TTL	Motion Control Module 1 PWM 6. This signal is controlled by Module 1 PWM Generator 3.
M1PWM7	43	PF3 (5)	0	TTL	Motion Control Module 1 PWM 7. This signal is controlled by Module 1 PWM Generator 3.
NMI	40 100	PF0 (8) PD7 (8)	I	TTL	Non-maskable interrupt.
OSC0	65	fixed	I	Analog	Main oscillator crystal input or an external clock reference input.
OSC1	66	fixed	0	Analog	Main oscillator crystal output. Leave unconnected when using a single-ended clock source.
PA0	26	-	I/O	TTL	GPIO port A bit 0.
PA1	27	-	I/O	TTL	GPIO port A bit 1.
PA2	28	-	I/O	TTL	GPIO port A bit 2.
PA3	29	-	I/O	TTL	GPIO port A bit 3.
PA4	30	-	I/O	TTL	GPIO port A bit 4.
PA5	31	-	I/O	TTL	GPIO port A bit 5.
PA6	34	-	I/O	TTL	GPIO port A bit 6.
PA7	35	-	I/O	TTL	GPIO port A bit 7.
PB0	70	-	I/O	TTL	GPIO port B bit 0. This pin is not 5-V tolerant.
PB1	71	-	I/O	TTL	GPIO port B bit 1. This pin is not 5-V tolerant.
PB2	72	-	I/O	TTL	GPIO port B bit 2.

Table 23-3. Signals by Signal Name (continued)

Pin Name	Pin Number	Pin Mux / Pin Assignment	Pin Type	Buffer Type ^a	Description
PB3	73	-	I/O	TTL	GPIO port B bit 3.
PB4	92	-	I/O	TTL	GPIO port B bit 4.
PB5	91	-	I/O	TTL	GPIO port B bit 5.
PC0	85	-	I/O	TTL	GPIO port C bit 0.
PC1	84	-	I/O	TTL	GPIO port C bit 1.
PC2	83	-	I/O	TTL	GPIO port C bit 2.
PC3	82	-	I/O	TTL	GPIO port C bit 3.
PC4	25	-	I/O	TTL	GPIO port C bit 4.
PC5	24	-	I/O	TTL	GPIO port C bit 5.
PC6	23	-	I/O	TTL	GPIO port C bit 6.
PC7	22	-	I/O	TTL	GPIO port C bit 7.
PD0	1	-	I/O	TTL	GPIO port D bit 0.
PD1	2	-	I/O	TTL	GPIO port D bit 1.
PD2	3	-	I/O	TTL	GPIO port D bit 2.
PD3	4	-	I/O	TTL	GPIO port D bit 3.
PD4	97	-	I/O	TTL	GPIO port D bit 4.
PD5	98	-	I/O	TTL	GPIO port D bit 5.
PD6	99	-	I/O	TTL	GPIO port D bit 6.
PD7	100	-	I/O	TTL	GPIO port D bit 7.
PE0	15	-	I/O	TTL	GPIO port E bit 0.
PE1	14	-	I/O	TTL	GPIO port E bit 1.
PE2	13	-	I/O	TTL	GPIO port E bit 2.
PE3	12	-	I/O	TTL	GPIO port E bit 3.
PE4	95	-	I/O	TTL	GPIO port E bit 4.
PE5	96	-	I/O	TTL	GPIO port E bit 5.
PE6	89	-	I/O	TTL	GPIO port E bit 6.
PE7	90	-	I/O	TTL	GPIO port E bit 7.
PF0	40	-	I/O	TTL	GPIO port F bit 0.
PF1	41	-	I/O	TTL	GPIO port F bit 1.
PF2	42	-	I/O	TTL	GPIO port F bit 2.
PF3	43	-	I/O	TTL	GPIO port F bit 3.
PF4	39	-	I/O	TTL	GPIO port F bit 4.
PF5	37	-	I/O	TTL	GPIO port F bit 5.
PF6	36	-	I/O	TTL	GPIO port F bit 6.
PF7	58	-	I/O	TTL	GPIO port F bit 7.
PG0	62	-	I/O	TTL	GPIO port G bit 0.
PG1	61	-	I/O	TTL	GPIO port G bit 1.
PG2	60	-	I/O	TTL	GPIO port G bit 2.
PG3	59	-	I/O	TTL	GPIO port G bit 3.
PG4	74	-	I/O	TTL	GPIO port G bit 4.
PG5	75	-	I/O	TTL	GPIO port G bit 5.

Table 23-3. Signals by Signal Name (continued)

Pin Name	Pin Number	Pin Mux / Pin Assignment	Pin Type	Buffer Type ^a	Description
PG6	87	-	I/O	TTL	GPIO port G bit 6.
PG7	88	-	I/O	TTL	GPIO port G bit 7.
PH0	16	-	I/O	TTL	GPIO port H bit 0.
PH1	17	-	I/O	TTL	GPIO port H bit 1.
PH2	18	-	I/O	TTL	GPIO port H bit 2.
РН3	19	-	I/O	TTL	GPIO port H bit 3.
РН4	79	-	I/O	TTL	GPIO port H bit 4.
РН5	78	-	I/O	TTL	GPIO port H bit 5.
РН6	77	-	I/O	TTL	GPIO port H bit 6.
РН7	76	-	I/O	TTL	GPIO port H bit 7.
PhA0	40 79 99	PF0 (6) PH4 (5) PD6 (6)	I	TTL	QEI module 0 phase A.
PhA1	24 59 62	PC5 (6) PG3 (6) PG0 (6)	I	TTL	QEI module 1 phase A.
PhB0	41 78 100	PF1 (6) PH5 (5) PD7 (6)	I	TTL	QEI module 0 phase B.
PhB1	23 61 74	PC6 (6) PG1 (6) PG4 (6)	I	TTL	QEI module 1 phase B.
PJ0	68	-	I/O	TTL	GPIO port J bit 0. This pin is not 5-V tolerant.
PJ1	69	-	I/O	TTL	GPIO port J bit 1. This pin is not 5-V tolerant.
PJ2	11	-	I/O	TTL	GPIO port J bit 2.
PK0	49	-	I/O	TTL	GPIO port K bit 0.
PK1	48	-	I/O	TTL	GPIO port K bit 1.
PK2	47	-	I/O	TTL	GPIO port K bit 2.
PK3	46	-	I/O	TTL	GPIO port K bit 3.
RST	63	fixed	ļ	TTL	System reset input.
SSI0Clk	28	PA2 (2)	I/O	TTL	SSI module 0 clock
SSI0Fss	29	PA3 (2)	I/O	TTL	SSI module 0 frame signal
SSI0Rx	30	PA4 (2)	I	TTL	SSI module 0 receive
SSIOTx	31	PA5 (2)	0	TTL	SSI module 0 transmit
SSI1Clk	1 42	PD0 (2) PF2 (2)	I/O	TTL	SSI module 1 clock.
SSI1Fss	2 43	PD1 (2) PF3 (2)	I/O	TTL	SSI module 1 frame signal.
SSI1Rx	3 40	PD2 (2) PF0 (2)	I	TTL	SSI module 1 receive.
SSI1Tx	4 41	PD3 (2) PF1 (2)	0	TTL	SSI module 1 transmit.
SSI2Clk	79 92	PH4 (2) PB4 (2)	I/O	TTL	SSI module 2 clock.

Table 23-3. Signals by Signal Name (continued)

Pin Name	Pin Number	Pin Mux / Pin Assignment	Pin Type	Buffer Type ^a	Description
SSI2Fss	78 91	PH5 (2) PB5 (2)	I/O	TTL	SSI module 2 frame signal.
SSI2Rx	77	PH6 (2)	I	TTL	SSI module 2 receive.
SSI2Tx	76	PH7 (2)	0	TTL	SSI module 2 transmit.
SSI3Clk	1 16 49	PD0 (1) PH0 (2) PK0 (2)	I/O	TTL	SSI module 3 clock.
SSI3Fss	2 17 48	PD1 (1) PH1 (2) PK1 (2)	I/O	TTL	SSI module 3 frame signal.
SSI3Rx	3 18 47	PD2 (1) PH2 (2) PK2 (2)	I	TTL	SSI module 3 receive.
SSI3Tx	4 19 46	PD3 (1) PH3 (2) PK3 (2)	0	TTL	SSI module 3 transmit.
SWCLK	85	PC0 (1)	I	TTL	JTAG/SWD CLK.
SWDIO	84	PC1 (1)	I/O	TTL	JTAG TMS and SWDIO.
SWO	82	PC3 (1)	0	TTL	JTAG TDO and SWO.
T0CCP0	40	PF0 (7)	I/O	TTL	16/32-Bit Timer 0 Capture/Compare/PWM 0.
TOCCP1	41	PF1 (7)	I/O	TTL	16/32-Bit Timer 0 Capture/Compare/PWM 1.
T1CCP0	42 68 92	PF2 (7) PJ0 (7) PB4 (7)	I/O	TTL	16/32-Bit Timer 1 Capture/Compare/PWM 0.
T1CCP1	43 69 91	PF3 (7) PJ1 (7) PB5 (7)	I/O	TTL	16/32-Bit Timer 1 Capture/Compare/PWM 1.
T2CCP0	11 39 70	PJ2 (7) PF4 (7) PB0 (7)	I/O	TTL	16/32-Bit Timer 2 Capture/Compare/PWM 0.
T2CCP1	37 71	PF5 (7) PB1 (7)	I/O	TTL	16/32-Bit Timer 2 Capture/Compare/PWM 1.
T3CCP0	36 72	PF6 (7) PB2 (7)	I/O	TTL	16/32-Bit Timer 3 Capture/Compare/PWM 0.
T3CCP1	58 73	PF7 (7) PB3 (7)	I/O	TTL	16/32-Bit Timer 3 Capture/Compare/PWM 1.
T4CCP0	62 85	PG0 (7) PC0 (7)	I/O	TTL	16/32-Bit Timer 4 Capture/Compare/PWM 0.
T4CCP1	61 84	PG1 (7) PC1 (7)	I/O	TTL	16/32-Bit Timer 4 Capture/Compare/PWM 1.
T5CCP0	60 83	PG2 (7) PC2 (7)	I/O	TTL	16/32-Bit Timer 5 Capture/Compare/PWM 0.
T5CCP1	59 82	PG3 (7) PC3 (7)	I/O	TTL	16/32-Bit Timer 5 Capture/Compare/PWM 1.
TCK	85	PC0 (1)	Ţ	TTL	JTAG/SWD CLK.
TDI	83	PC2 (1)	I	TTL	JTAG TDI.
TDO	82	PC3 (1)	0	TTL	JTAG TDO and SWO.

Table 23-3. Signals by Signal Name (continued)

Pin Name	Pin Number	Pin Mux / Pin Assignment	Pin Type	Buffer Type ^a	Description
TMS	84	PC1 (1)	I	TTL	JTAG TMS and SWDIO.
TRCLK	43	PF3 (14)	0	TTL	Trace clock.
TRD0	42	PF2 (14)	0	TTL	Trace data 0.
TRD1	41	PF1 (14)	0	TTL	Trace data 1.
TRD2	40	PF0 (14)	0	TTL	Trace data 2.
TRD3	39	PF4 (14)	0	TTL	Trace data 3.
UORx	26	PA0 (1)	1	TTL	UART module 0 receive.
UOTx	27	PA1 (1)	0	TTL	UART module 0 transmit.
U1CTS	24 41	PC5 (8) PF1 (1)	I	TTL	UART module 1 Clear To Send modem flow control input signal.
U1DCD	42	PF2 (1)	I	TTL	UART module 1 Data Carrier Detect modem status input signal.
U1DSR	43	PF3 (1)	I	TTL	UART module 1 Data Set Ready modem output control line.
U1DTR	39	PF4 (1)	0	TTL	UART module 1 Data Terminal Ready modem status input signal.
U1RI	90	PE7 (1)	I	TTL	UART module 1 Ring Indicator modem status input signal.
U1RTS	25 40	PC4 (8) PF0 (1)	0	TTL	UART module 1 Request to Send modem flow control output line.
U1Rx	25 70	PC4 (2) PB0 (1)	I	TTL	UART module 1 receive.
UlTx	24 71	PC5 (2) PB1 (1)	0	TTL	UART module 1 transmit.
U2Rx	74 99	PG4 (1) PD6 (1)	I	TTL	UART module 2 receive.
U2Tx	75 100	PG5 (1) PD7 (1)	0	TTL	UART module 2 transmit.
U3Rx	23	PC6 (1)	I	TTL	UART module 3 receive.
U3Tx	22	PC7 (1)	0	TTL	UART module 3 transmit.
U4Rx	25 68	PC4 (1) PJ0 (1)	I	TTL	UART module 4 receive.
U4Tx	24 69	PC5 (1) PJ1 (1)	0	TTL	UART module 4 transmit.
U5Rx	11 95	PJ2 (1) PE4 (1)	I	TTL	UART module 5 receive.
U5Tx	96	PE5 (1)	0	TTL	UART module 5 transmit.
U6Rx	97	PD4 (1)	I	TTL	UART module 6 receive.
U6Tx	98	PD5 (1)	0	TTL	UART module 6 transmit.
U7Rx	15	PE0 (1)	I	TTL	UART module 7 receive.
U7Tx	14	PE1 (1)	0	TTL	UART module 7 transmit.
USB0DM	68	PJ0	I/O	Analog	Bidirectional differential data pin (D- per USB specification) for USB0.
USB0DP	69	PJ1	I/O	Analog	Bidirectional differential data pin (D+ per USB specification) for USB0.

Table 23-3. Signals by Signal Name (continued)

Pin Name	Pin Number	Pin Mux / Pin	Pin Type	Buffer Type ^a	Description
		Assignment			
USB0EPEN	3 23 39 74	PD2 (8) PC6 (8) PF4 (8) PG4 (8)	0	TTL	Optionally used in Host mode to control an external power source to supply power to the USB bus.
USB0ID	70	PB0	I	Analog	This signal senses the state of the USB ID signal. The USB PHY enables an integrated pull-up, and an external element (USB connector) indicates the initial state of the USB controller (pulled down is the A side of the cable and pulled up is the B side).
USB0PFLT	4 22 37 75	PD3 (8) PC7 (8) PF5 (8) PG5 (8)	I	TTL	Optionally used in Host mode by an external power source to indicate an error state by that power source.
USB0VBUS	71	PB1	I/O	Analog	This signal is used during the session request protocol. This signal allows the USB PHY to both sense the voltage level of VBUS, and pull up VBUS momentarily during VBUS pulsing.
VBAT	55	fixed	-	Power	Power source for the Hibernation module. It is normally connected to the positive terminal of a battery and serves as the battery backup/Hibernation module power-source supply.
VDD	5 20 32 44 56 67 80 93	fixed	-	Power	Positive supply for I/O and some logic.
VDDA	7	fixed	-	Power	The positive supply for the analog circuits (ADC, Analog Comparators, etc.). These are separated from VDD to minimize the electrical noise contained on VDD from affecting the analog functions. VDDA pins must be supplied with a voltage that meets the specification in Table 24-5 on page 1378, regardless of system implementation.
VDDC	38 86	fixed	-	Power	Positive supply for most of the logic function, including the processor core and most peripherals. The voltage on this pin is 1.2 V and is supplied by the on-chip LDO. The VDDC pins should only be connected to each other and an external capacitor as specified in Table 24-12 on page 1390 .
VREFA+	8	fixed	-	Analog	A reference voltage used to specify the voltage at which the ADC converts to a maximum value. This pin is used in conjunction with $\mathtt{VREFA-}$ which specifies the minimum value. In other words, the voltage that is applied to $\mathtt{VREFA+}$ is the voltage with which an \mathtt{AINn} signal is converted to 4095. The $\mathtt{VREFA+}$ voltage is limited to the range specified in Table 24-31 on page 1403 .

Table 23-3. Signals by Signal Name (continued)

Pin Name	Pin Number	Pin Mux / Pin Assignment	Pin Type	Buffer Type ^a	Description
VREFA-	9	fixed	-	Analog	A reference voltage used to specify the input voltage at which the ADC converts to a minimum value. This pin is used in conjunction with VREFA+ which specifies the maximum value. In other words, the voltage that is applied to VREFA- is the voltage with which an AINn signal is converted to 0, while the voltage that is applied to VREFA+ is the voltage with which an AINn signal is converted to 4095. The VREFA- voltage is limited to the range specified in Table 24-31 on page 1403.
WAKE	50	fixed	I	TTL	An external input that brings the processor out of Hibernate mode when asserted.
WT0CCP0	25 74	PC4 (7) PG4 (7)	I/O	TTL	32/64-Bit Wide Timer 0 Capture/Compare/PWM 0.
WT0CCP1	24 75	PC5 (7) PG5 (7)	I/O	TTL	32/64-Bit Wide Timer 0 Capture/Compare/PWM 1.
WT1CCP0	23 87	PC6 (7) PG6 (7)	I/O	TTL	32/64-Bit Wide Timer 1 Capture/Compare/PWM 0.
WT1CCP1	22 88	PC7 (7) PG7 (7)	I/O	TTL	32/64-Bit Wide Timer 1 Capture/Compare/PWM 1.
WT2CCP0	1 16	PD0 (7) PH0 (7)	I/O	TTL	32/64-Bit Wide Timer 2 Capture/Compare/PWM 0.
WT2CCP1	2 17	PD1 (7) PH1 (7)	I/O	TTL	32/64-Bit Wide Timer 2 Capture/Compare/PWM 1.
WT3CCP0	3 79	PD2 (7) PH4 (7)	I/O	TTL	32/64-Bit Wide Timer 3 Capture/Compare/PWM 0.
WT3CCP1	4 78	PD3 (7) PH5 (7)	I/O	TTL	32/64-Bit Wide Timer 3 Capture/Compare/PWM 1.
WT4CCP0	77 97	PH6 (7) PD4 (7)	I/O	TTL	32/64-Bit Wide Timer 4 Capture/Compare/PWM 0.
WT4CCP1	76 98	PH7 (7) PD5 (7)	I/O	TTL	32/64-Bit Wide Timer 4 Capture/Compare/PWM 1.
WT5CCP0	18 99	PH2 (7) PD6 (7)	I/O	TTL	32/64-Bit Wide Timer 5 Capture/Compare/PWM 0.
WT5CCP1	19 100	PH3 (7) PD7 (7)	I/O	TTL	32/64-Bit Wide Timer 5 Capture/Compare/PWM 1.
xosc0	52	fixed	I	Analog	Hibernation module oscillator crystal input or an external clock reference input. Note that this is either a 32.768-kHz crystal or a 32.768-kHz oscillator for the Hibernation module RTC.
XOSC1	54	fixed	0	Analog	Hibernation module oscillator crystal output. Leave unconnected when using a single-ended clock source.

a. The TTL designation indicates the pin has TTL-compatible voltage levels.

23.3 Signals by Function, Except for GPIO

Table 23-4. Signals by Function, Except for GPIO

Function	Pin Name	Pin Number	Pin Type	Buffer Type ^a	Description
	AIN0	12	I	Analog	Analog-to-digital converter input 0.
	AIN1	13	I	Analog	Analog-to-digital converter input 1.
	AIN2	14	I	Analog	Analog-to-digital converter input 2.
	AIN3	15	I	Analog	Analog-to-digital converter input 3.
	AIN4	100	I	Analog	Analog-to-digital converter input 4.
	AIN5	99	I	Analog	Analog-to-digital converter input 5.
	AIN6	98	I	Analog	Analog-to-digital converter input 6.
	AIN7	97	I	Analog	Analog-to-digital converter input 7.
	AIN8	96	I	Analog	Analog-to-digital converter input 8.
	AIN9	95	I	Analog	Analog-to-digital converter input 9.
	AIN10	92	I	Analog	Analog-to-digital converter input 10.
	AIN11	91	I	Analog	Analog-to-digital converter input 11.
	AIN12	4	I	Analog	Analog-to-digital converter input 12.
	AIN13	3	I	Analog	Analog-to-digital converter input 13.
	AIN14	2	I	Analog	Analog-to-digital converter input 14.
	AIN15	1	I	Analog	Analog-to-digital converter input 15.
	AIN16	16	I	Analog	Analog-to-digital converter input 16.
ADC	AIN17	17	I	Analog	Analog-to-digital converter input 17.
	AIN18	18	I	Analog	Analog-to-digital converter input 18.
	AIN19	19	I	Analog	Analog-to-digital converter input 19.
	AIN20	90	I	Analog	Analog-to-digital converter input 20.
	AIN21	89	I	Analog	Analog-to-digital converter input 21.
	VREFA+	8	-	Analog	A reference voltage used to specify the voltage at which the ADC converts to a maximum value. This pin is used in conjunction with $\mathtt{VREFA-}$ which specifies the minimum value. In other words, the voltage that is applied to $\mathtt{VREFA+}$ is the voltage with which an \mathtt{AINn} signal is converted to 4095. The $\mathtt{VREFA+}$ voltage is limited to the range specified in Table 24-31 on page 1403 .
	VREFA-	9	-	Analog	A reference voltage used to specify the input voltage at which the ADC converts to a minimum value. This pin is used in conjunction with VREFA+ which specifies the maximum value. In other words, the voltage that is applied to VREFA- is the voltage with which an AINn signal is converted to 0, while the voltage that is applied to VREFA+ is the voltage with which an AINn signal is converted to 4095. The VREFA- voltage is limited to the range specified in Table 24-31 on page 1403.

Table 23-4. Signals by Function, Except for GPIO (continued)

Function	Pin Name	Pin Number	Pin Type	Buffer Type ^a	Description
	C0+	23	Į	Analog	Analog comparator 0 positive input.
	C0-	22	I	Analog	Analog comparator 0 negative input.
	C0o	40	0	TTL	Analog comparator 0 output.
	C1+	24	ļ	Analog	Analog comparator 1 positive input.
Analog Comparators	C1-	25	Į	Analog	Analog comparator 1 negative input.
	Clo	41	0	TTL	Analog comparator 1 output.
	C2+	87	I	Analog	Analog comparator 2 positive input.
	C2-	88	ļ	Analog	Analog comparator 2 negative input.
	C2o	42	0	TTL	Analog comparator 2 output.
	CAN0Rx	40 92 95	I	TTL	CAN module 0 receive.
Controller Area Network	CAN0Tx	43 91 96	0	TTL	CAN module 0 transmit.
	CAN1Rx	26 89	I	TTL	CAN module 1 receive.
	CAN1Tx	27 90	0	TTL	CAN module 1 transmit.
	TRCLK	43	0	TTL	Trace clock.
	TRD0	42	0	TTL	Trace data 0.
Core	TRD1	41	0	TTL	Trace data 1.
	TRD2	40	0	TTL	Trace data 2.
	TRD3	39	0	TTL	Trace data 3.

Table 23-4. Signals by Function, Except for GPIO (continued)

Function	Pin Name	Pin Number	Pin Type	Buffer Type ^a	Description
	TOCCPO	40	I/O	TTL	16/32-Bit Timer 0 Capture/Compare/PWM 0.
	T0CCP1	41	I/O	TTL	16/32-Bit Timer 0 Capture/Compare/PWM 1.
	T1CCP0	42 68 92	I/O	TTL	16/32-Bit Timer 1 Capture/Compare/PWM 0.
	T1CCP1	43 69 91	I/O	TTL	16/32-Bit Timer 1 Capture/Compare/PWM 1.
	T2CCP0	11 39 70	I/O	TTL	16/32-Bit Timer 2 Capture/Compare/PWM 0.
	T2CCP1	37 71	I/O	TTL	16/32-Bit Timer 2 Capture/Compare/PWM 1.
	T3CCP0	36 72	I/O	TTL	16/32-Bit Timer 3 Capture/Compare/PWM 0.
	T3CCP1	58 73	I/O	TTL	16/32-Bit Timer 3 Capture/Compare/PWM 1.
	T4CCP0	62 85	I/O	TTL	16/32-Bit Timer 4 Capture/Compare/PWM 0.
	T4CCP1	61 84	I/O	TTL	16/32-Bit Timer 4 Capture/Compare/PWM 1.
	T5CCP0	60 83	I/O	TTL	16/32-Bit Timer 5 Capture/Compare/PWM 0.
General-Purpose Timers	T5CCP1	59 82	I/O	TTL	16/32-Bit Timer 5 Capture/Compare/PWM 1.
Timers	WT0CCP0	25 74	I/O	TTL	32/64-Bit Wide Timer 0 Capture/Compare/PWM 0.
	WT0CCP1	24 75	I/O	TTL	32/64-Bit Wide Timer 0 Capture/Compare/PWM 1.
	WT1CCP0	23 87	I/O	TTL	32/64-Bit Wide Timer 1 Capture/Compare/PWM 0.
	WT1CCP1	22 88	I/O	TTL	32/64-Bit Wide Timer 1 Capture/Compare/PWM 1.
	WT2CCP0	1 16	I/O	TTL	32/64-Bit Wide Timer 2 Capture/Compare/PWM 0.
	WT2CCP1	2 17	I/O	TTL	32/64-Bit Wide Timer 2 Capture/Compare/PWM 1.
	WT3CCP0	3 79	I/O	TTL	32/64-Bit Wide Timer 3 Capture/Compare/PWM 0.
	WT3CCP1	4 78	I/O	TTL	32/64-Bit Wide Timer 3 Capture/Compare/PWM 1.
	WT4CCP0	77 97	I/O	TTL	32/64-Bit Wide Timer 4 Capture/Compare/PWM 0.
	WT4CCP1	76 98	I/O	TTL	32/64-Bit Wide Timer 4 Capture/Compare/PWM 1.
	WT5CCP0	18 99	I/O	TTL	32/64-Bit Wide Timer 5 Capture/Compare/PWM 0.
	WT5CCP1	19 100	I/O	TTL	32/64-Bit Wide Timer 5 Capture/Compare/PWM 1.

Table 23-4. Signals by Function, Except for GPIO (continued)

Function	Pin Name	Pin Number	Pin Type	Buffer Type ^a	Description
	GNDX	53	-	Power	GND for the Hibernation oscillator. When using a crystal clock source, this pin should only be connected to the crystal load capacitors to improve oscillator immunity to system noise. When using an external oscillator, this pin should be connected to GND.
	HIB	51	0	TTL	An output that indicates the processor is in Hibernate mode.
Hibernate	VBAT	55	-	Power	Power source for the Hibernation module. It is normally connected to the positive terminal of a battery and serves as the battery backup/Hibernation module power-source supply.
	WAKE	50	I	TTL	An external input that brings the processor out of Hibernate mode when asserted.
	xosc0	52	I	Analog	Hibernation module oscillator crystal input or an external clock reference input. Note that this is either a 32.768-kHz crystal or a 32.768-kHz oscillator for the Hibernation module RTC.
	xosc1	54	0	Analog	Hibernation module oscillator crystal output. Leave unconnected when using a single-ended clock source.
	I2C0SCL	72	I/O	OD	I ² C module 0 clock. Note that this signal has an active pull-up. The corresponding port pin should not be configured as open drain.
	I2C0SDA	73	I/O	OD	I ² C module 0 data.
	I2C1SCL	34 74	I/O	OD	I ² C module 1 clock. Note that this signal has an active pull-up. The corresponding port pin should not be configured as open drain.
	I2C1SDA	35 75	I/O	OD	I ² C module 1 data.
	I2C2SCL	36 95	I/O	OD	I ² C module 2 clock. Note that this signal has an active pull-up. The corresponding port pin should not be configured as open drain.
12C	I2C2SDA	58 96	I/O	OD	I ² C module 2 data.
	I2C3SCL	1 62	I/O	OD	I ² C module 3 clock. Note that this signal has an active pull-up. The corresponding port pin should not be configured as open drain.
	I2C3SDA	2 61	I/O	OD	I ² C module 3 data.
	I2C4SCL	60	I/O	OD	I ² C module 4 clock. Note that this signal has an active pull-up. The corresponding port pin should not be configured as open drain.
	I2C4SDA	59	I/O	OD	I ² C module 4 data.
	I2C5SCL	87	I/O	OD	I ² C module 5 clock. Note that this signal has an active pull-up. The corresponding port pin should not be configured as open drain.
	I2C5SDA	88	I/O	OD	I ² C module 5 data.

Table 23-4. Signals by Function, Except for GPIO (continued)

Function	Pin Name	Pin Number	Pin Type	Buffer Type ^a	Description
	SWCLK	85	I	TTL	JTAG/SWD CLK.
	SWDIO	84	I/O	TTL	JTAG TMS and SWDIO.
	SWO	82	0	TTL	JTAG TDO and SWO.
JTAG/SWD/SWO	TCK	85	I	TTL	JTAG/SWD CLK.
	TDI	83	ļ	TTL	JTAG TDI.
	TDO	82	0	TTL	JTAG TDO and SWO.
	TMS	84	I	TTL	JTAG TMS and SWDIO.

Table 23-4. Signals by Function, Except for GPIO (continued)

Function	Pin Name	Pin Number	Pin Type	Buffer Type ^a	Description
	M0FAULT0	3 16 42 99	I	TTL	Motion Control Module 0 PWM Fault 0.
	M0FAULT1	17 43 60 100	I	TTL	Motion Control Module 0 PWM Fault 1.
	M0FAULT2	18 39 59	I	TTL	Motion Control Module 0 PWM Fault 2.
	MOFAULT3	19 37	I	TTL	Motion Control Module 0 PWM Fault 3.
	моримо	16	0	TTL	Motion Control Module 0 PWM 0. This signal is controlled by Module 0 PWM Generator 0.
	M0PWM1	17	0	TTL	Motion Control Module 0 PWM 1. This signal is controlled by Module 0 PWM Generator 0.
	морим2	18 92	0	TTL	Motion Control Module 0 PWM 2. This signal is controlled by Module 0 PWM Generator 1.
	морим3	19 91	0	TTL	Motion Control Module 0 PWM 3. This signal is controlled by Module 0 PWM Generator 1.
	MOPWM4	74 79 95	0	TTL	Motion Control Module 0 PWM 4. This signal is controlled by Module 0 PWM Generator 2.
PWM	морwм5	75 78 96	0	TTL	Motion Control Module 0 PWM 5. This signal is controlled by Module 0 PWM Generator 2.
	морим6	1 25 77 87	0	TTL	Motion Control Module 0 PWM 6. This signal is controlled by Module 0 PWM Generator 3.
	морим7	2 24 76 88	0	TTL	Motion Control Module 0 PWM 7. This signal is controlled by Module 0 PWM Generator 3.
	M1FAULT0	39 49 58	I	TTL	Motion Control Module 1 PWM Fault 0.
	M1FAULT1	48 62	I	TTL	Motion Control Module 1 PWM Fault 1.
	M1FAULT2	47 61	I	TTL	Motion Control Module 1 PWM Fault 2.
	M1FAULT3	46	Ι	TTL	Motion Control Module 1 PWM Fault 3.
	M1PWM0	1 60	0	TTL	Motion Control Module 1 PWM 0. This signal is controlled by Module 1 PWM Generator 0.
	M1PWM1	2 59	0	TTL	Motion Control Module 1 PWM 1. This signal is controlled by Module 1 PWM Generator 0.
	M1PWM2	34 74 95	0	TTL	Motion Control Module 1 PWM 2. This signal is controlled by Module 1 PWM Generator 1.
	M1PWM3		0	TTL	

Table 23-4. Signals by Function, Except for GPIO (continued)

Function	Pin Name	Pin Number	Pin Type	Buffer Type ^a	Description
		35 75 96			Motion Control Module 1 PWM 3. This signal is controlled by Module 1 PWM Generator 1.
	M1PWM4	40	0	TTL	Motion Control Module 1 PWM 4. This signal is controlled by Module 1 PWM Generator 2.
	M1PWM5	41	0	TTL	Motion Control Module 1 PWM 5. This signal is controlled by Module 1 PWM Generator 2.
	M1PWM6	42	0	TTL	Motion Control Module 1 PWM 6. This signal is controlled by Module 1 PWM Generator 3.
	M1PWM7	43	0	TTL	Motion Control Module 1 PWM 7. This signal is controlled by Module 1 PWM Generator 3.
	GND	6 21 33 45 57 64 81 94	-	Power	Ground reference for logic and I/O pins.
	GNDA	10	-	Power	The ground reference for the analog circuits (ADC, Analog Comparators, etc.). These are separated from GND to minimize the electrical noise contained on VDD from affecting the analog functions.
Power	VDD	5 20 32 44 56 67 80 93	-	Power	Positive supply for I/O and some logic.
	VDDA	7	-	Power	The positive supply for the analog circuits (ADC, Analog Comparators, etc.). These are separated from VDD to minimize the electrical noise contained on VDD from affecting the analog functions. VDDA pins must be supplied with a voltage that meets the specification in Table 24-5 on page 1378, regardless of system implementation.
	VDDC	38 86	-	Power	Positive supply for most of the logic function, including the processor core and most peripherals. The voltage on this pin is 1.2 V and is supplied by the on-chip LDO. The VDDC pins should only be connected to each other and an external capacitor as specified in Table 24-12 on page 1390.

Table 23-4. Signals by Function, Except for GPIO (continued)

Function	Pin Name	Pin Number	Pin Type	Buffer Type ^a	Description
	IDX0	4 11 17 39	I	TTL	QEI module 0 index.
	IDX1	25 75 88	I	TTL	QEI module 1 index.
QEI	PhA0	40 79 99	I	TTL	QEI module 0 phase A.
	PhA1	24 59 62	I	TTL	QEI module 1 phase A.
	PhB0	41 78 100	I	TTL	QEI module 0 phase B.
	PhB1	23 61 74	I	TTL	QEI module 1 phase B.
	SSI0Clk	28	I/O	TTL	SSI module 0 clock
	SSI0Fss	29	I/O	TTL	SSI module 0 frame signal
	SSIORx	30	I	TTL	SSI module 0 receive
	SSI0Tx	31	0	TTL	SSI module 0 transmit
	SSI1Clk	1 42	I/O	TTL	SSI module 1 clock.
	SSI1Fss	2 43	I/O	TTL	SSI module 1 frame signal.
	SSI1Rx	3 40	I	TTL	SSI module 1 receive.
	SSI1Tx	4 41	0	TTL	SSI module 1 transmit.
	SSI2Clk	79 92	I/O	TTL	SSI module 2 clock.
SSI	SSI2Fss	78 91	I/O	TTL	SSI module 2 frame signal.
	SSI2Rx	77	I	TTL	SSI module 2 receive.
	SSI2Tx	76	0	TTL	SSI module 2 transmit.
	SSI3Clk	1 16 49	I/O	TTL	SSI module 3 clock.
	SSI3Fss	2 17 48	I/O	TTL	SSI module 3 frame signal.
	SSI3Rx	3 18 47	I	TTL	SSI module 3 receive.
	SSI3Tx	4 19 46	0	TTL	SSI module 3 transmit.

Table 23-4. Signals by Function, Except for GPIO (continued)

Function	Pin Name	Pin Number	Pin Type	Buffer Type ^a	Description
	NMI	40 100	I	TTL	Non-maskable interrupt.
System Control & Clocks	osc0	65	I	Analog	Main oscillator crystal input or an external clock reference input.
CIOCKS	osc1	66	0	Analog	Main oscillator crystal output. Leave unconnected when using a single-ended clock source.
	RST	63	I	TTL	System reset input.
	U0Rx	26	I	TTL	UART module 0 receive.
	UOTx	27	0	TTL	UART module 0 transmit.
	U1CTS	24 41	I	TTL	UART module 1 Clear To Send modem flow control input signal.
	U1DCD	42	I	TTL	UART module 1 Data Carrier Detect modem status input signal.
	U1DSR	43	I	TTL	UART module 1 Data Set Ready modem output control line.
	U1DTR	39	0	TTL	UART module 1 Data Terminal Ready modem status input signal.
	U1RI	90	I	TTL	UART module 1 Ring Indicator modem status input signal.
	U1RTS	25 40	0	TTL	UART module 1 Request to Send modem flow control output line.
	U1Rx	25 70	I	TTL	UART module 1 receive.
LIADT	UlTx	24 71	0	TTL	UART module 1 transmit.
UART	U2Rx	74 99	I	TTL	UART module 2 receive.
	U2Tx	75 100	0	TTL	UART module 2 transmit.
	U3Rx	23	I	TTL	UART module 3 receive.
	U3Tx	22	0	TTL	UART module 3 transmit.
	U4Rx	25 68	I	TTL	UART module 4 receive.
	U4Tx	24 69	0	TTL	UART module 4 transmit.
	U5Rx	11 95	I	TTL	UART module 5 receive.
	U5Tx	96	0	TTL	UART module 5 transmit.
	U6Rx	97	I	TTL	UART module 6 receive.
	U6Tx	98	0	TTL	UART module 6 transmit.
	U7Rx	15	I	TTL	UART module 7 receive.
	U7Tx	14	0	TTL	UART module 7 transmit.

Table 23-4. Signals by Function, Except for GPIO (continued)

Function	Pin Name	Pin Number	Pin Type	Buffer Type ^a	Description
	USB0DM	68	I/O	Analog	Bidirectional differential data pin (D- per USB specification) for USB0.
	USB0DP	69	I/O	Analog	Bidirectional differential data pin (D+ per USB specification) for USB0.
	USB0EPEN	3 23 39 74	0	TTL	Optionally used in Host mode to control an external power source to supply power to the USB bus.
USB	USB0ID	70	I	Analog	This signal senses the state of the USB ID signal. The USB PHY enables an integrated pull-up, and an external element (USB connector) indicates the initial state of the USB controller (pulled down is the A side of the cable and pulled up is the B side).
	USB0PFLT	4 22 37 75	I	TTL	Optionally used in Host mode by an external power source to indicate an error state by that power source.
	USB0VBUS	71	I/O	Analog	This signal is used during the session request protocol. This signal allows the USB PHY to both sense the voltage level of VBUS, and pull up VBUS momentarily during VBUS pulsing.

a. The TTL designation indicates the pin has TTL-compatible voltage levels.

23.4 GPIO Pins and Alternate Functions

Table 23-5. GPIO Pins and Alternate Functions

Ю	Pin	Analog Function	Digital Function (GPIOPCTL PMCx Bit Field Encoding) ^a											
			1	2	3	4	5	6	7	8	9	14	15	
PA0	26	-	U0Rx	-	-	-	-	-	-	CAN1Rx	-	-	-	
PA1	27	-	U0Tx	-	-	-	-	-	-	CAN1Tx	-	-	-	
PA2	28	-	-	SSI0Clk	-	-	-	-	-	-	-	-	-	
PA3	29	-	-	SSI0Fss	-	-	-	-	-	-	-	-	-	
PA4	30	-	-	SSI0Rx	-	-	-	-	-	-	-	-	-	
PA5	31	-	-	SSIOTx	-	-	-	-	-	-	-	-	-	
PA6	34	-	-	-	I2C1SCL	-	M1PWM2	-	-	-	-	-	-	
PA7	35	-	-	-	I2C1SDA	-	м1рwм3	-	-	-	-	-	-	
PB0	70	USB0ID	U1Rx	-	-	-	-	-	T2CCP0	-	-	-	-	
PB1	71	USB0VBUS	UlTx	-	-	-	-	-	T2CCP1	-	-	-	-	
PB2	72	-	-	-	I2C0SCL	-	-	-	T3CCP0	-	-	-	-	
PB3	73	-	-	-	I2C0SDA	-	-	-	T3CCP1	-	-	-	-	
PB4	92	AIN10	-	SSI2Clk	-	M0PWM2	-	-	T1CCP0	CAN0Rx	-	-	-	
PB5	91	AIN11	-	SSI2Fss	-	морwм3	-	-	T1CCP1	CAN0Tx	-	-	-	
PC0	85	-	TCK SWCLK	-	-	-	-	-	T4CCP0	-	-	-	-	
PC1	84	-	TMS SWDIO	-	-	-	-	-	T4CCP1	-	-	-	-	
PC2	83	-	TDI	-	-	-	-	-	T5CCP0	-	-	-	-	

Table 23-5. GPIO Pins and Alternate Functions (continued)

Ю	Pin	Analog													
		Function	1	2	3	4	5	6	7	8	9	14	15		
PC3	82	-	TDO SWO	-	-	-	-	-	T5CCP1	-	-	-	-		
PC4	25	C1-	U4Rx	U1Rx	-	морwм6	-	IDX1	WT0CCP0	Ulrts	-	-	-		
PC5	24	C1+	U4Tx	U1Tx	-	морим7	-	PhA1	WT0CCP1	U1CTS	-	-	-		
PC6	23	C0+	U3Rx	-	-	-	-	PhB1	WT1CCP0	USB0EPEN	-	-	-		
PC7	22	C0-	U3Tx	-	-	-	-	-	WT1CCP1	USB0PFLT	-	-	-		
PD0	1	AIN15	SSI3Clk	SSI1Clk	I2C3SCL	морwм6	M1PWM0	-	WT2CCP0	-	-	-	-		
PD1	2	AIN14	SSI3Fss	SSI1Fss	I2C3SDA	морим7	M1PWM1	-	WT2CCP1	-	-	-	-		
PD2	3	AIN13	SSI3Rx	SSI1Rx	-	MOFAULTO	-	-	WT3CCP0	USB0EPEN	-	-	-		
PD3	4	AIN12	SSI3Tx	SSI1Tx	-	-	-	IDX0	WT3CCP1	USB0PFLT	-	-	-		
PD4	97	AIN7	U6Rx	-	-	-	-	-	WT4CCP0	-	-	-	-		
PD5	98	AIN6	U6Tx	-	-	-	-	-	WT4CCP1	-	-	-	-		
PD6	99	AIN5	U2Rx	-	-	MOFAULTO	-	PhA0	WT5CCP0	-	-	-	-		
PD7	100	AIN4	U2Tx	-	-	MOFAULT1	-	PhB0	WT5CCP1	NMI	-	-	-		
PE0	15	AIN3	U7Rx	-	-	-	-	-	-	-	-	-	-		
PE1	14	AIN2	U7Tx	-	-	-	-	-	-	-	-	-	-		
PE2	13	AIN1	-	-	-	-	-	-	-	-	-	-	-		
PE3	12	AIN0	-	-	-	-	-	-	-	-	-	-	-		
PE4	95	AIN9	U5Rx	-	I2C2SCL	морим4	M1PWM2	-	-	CAN0Rx	-	-	-		
PE5	96	AIN8	U5Tx	-	I2C2SDA	морwм5	M1PWM3	-	-	CAN0Tx	-	-	-		
PE6	89	AIN21	-	-	-	-	-	-	-	CAN1Rx	-	-	-		
PE7	90	AIN20	U1RI	-	-	-	-	-	-	CAN1Tx	-	-	-		
PF0	40	-	U1RTS	SSI1Rx	CAN0Rx	-	M1PWM4	PhA0	T0CCP0	NMI	C0o	TRD2	-		
PF1	41	-	U1CTS	SSI1Tx	-	-	M1PWM5	PhB0	T0CCP1	-	C1o	TRD1	-		
PF2	42	-	U1DCD	SSI1Clk	-	MOFAULTO	M1PWM6	-	T1CCP0	-	C20	TRD0	-		
PF3	43	-	U1DSR	SSI1Fss	CAN0Tx	MOFAULT1	M1PWM7	-	T1CCP1	-	-	TRCLK	-		
PF4	39	-	U1DTR	-	-	MOFAULT2	M1FAULT0	IDX0	T2CCP0	USB0EPEN	-	TRD3	-		
PF5	37	-	-	-	-	MOFAULT3	-	-	T2CCP1	USB0PFLT	-	-	-		
PF6	36	-	-	-	I2C2SCL	-	-	-	T3CCP0	-	-	-	-		
PF7	58	-	-	-	I2C2SDA	-	M1FAULT0	-	T3CCP1	-	-	-	-		
PG0	62	-	-	-	I2C3SCL	-	M1FAULT1	PhA1	T4CCP0	-	-	-	-		
PG1	61	-	-	-	I2C3SDA	-	M1FAULT2	PhB1	T4CCP1	-	-	-	-		
PG2	60	-	-	-	I2C4SCL	MOFAULT1	M1PWM0	-	T5CCP0	-	-	-	-		
PG3	59	-	-	-	I2C4SDA	M0FAULT2	M1PWM1	PhA1	T5CCP1	-	-	-	-		
PG4	74	-	U2Rx	-	I2C1SCL	морум4	M1PWM2	PhB1	WT0CCP0	USB0EPEN	-	-	-		
PG5	75	-	U2Tx	-	I2C1SDA	морум5	M1PWM3	IDX1	WT0CCP1	USB0PFLT	-	-	-		
PG6	87	C2+	-	-	I2C5SCL	морwм6	-	-	WT1CCP0	-	-	-	-		
PG7	88	C2-	-	-	I2C5SDA	морwм7	IDX1	-	WT1CCP1	-	-	-	-		
PH0	16	AIN16	-	SSI3Clk	-	моримо	-	MOFAULTO	WT2CCP0	-	-	-	-		
PH1	17	AIN17	-	SSI3Fss	-	M0PWM1	IDX0	MOFAULT1	WT2CCP1	-	-	-	-		

Table 23-5. GPIO Pins and Alternate Functions (continued)

10	Pin	Analog			Dig	ital Functi	on (GPIO	PCTL PM	Cx Bit Fiel	d Encodi	ng) ^a		
10		Function	1	2	3	4	5	6	7	8	9	14	15
PH2	18	AIN18	-	SSI3Rx	-	морим2	-	M0FAULT2	WT5CCP0	-	-	-	-
РН3	19	AIN19	-	SSI3Tx	-	моримз	-	MOFAULT3	WT5CCP1	-	-	-	-
PH4	79	-	-	SSI2Clk	-	морим4	PhA0	-	WT3CCP0	-	-	-	-
PH5	78	-	-	SSI2Fss	-	морим5	PhB0	-	WT3CCP1	-	-	-	-
РН6	77	-	-	SSI2Rx	-	моримб	-	-	WT4CCP0	-	-	-	-
PH7	76	-	-	SSI2Tx	-	морим7	-	-	WT4CCP1	-	-	-	-
рј0	68	USB0DM	U4Rx	-	-	-	-	-	T1CCP0	-	-	-	-
PJ1	69	USB0DP	U4Tx	-	-	-	-	-	T1CCP1	-	-	-	-
РЈ2	11	-	U5Rx	-	-	-	IDX0	-	T2CCP0	-	-	-	-
PK0	49	-	-	SSI3Clk	-	-	-	M1FAULT0	-	-	-	-	-
PK1	48	-	-	SSI3Fss	-	-	-	M1FAULT1	-	-	-	-	-
PK2	47	-	-	SSI3Rx	-	-	-	M1FAULT2	-	-	-	-	-
PK3	46	-	-	SSI3Tx	-	-	-	M1FAULT3	-	-	-	-	-

a. The digital signals that are shaded gray are the power-on default values for the corresponding GPIO pin. Encodings 10-13 are not used on this device.

23.5 Possible Pin Assignments for Alternate Functions

Table 23-6. Possible Pin Assignments for Alternate Functions

# of Possible Assignments	Alternate Function	GPIO Function
	AIN0	PE3
	AIN1	PE2
	AIN10	PB4
	AIN11	PB5
	AIN12	PD3
	AIN13	PD2
	AIN14	PD1
	AIN15	PD0
	AIN16	PH0
	AIN17	PH1
	AIN18	PH2
	AIN19	PH3
	AIN2	PE1
	AIN20	PE7
	AIN21	PE6
	AIN3	PE0
	AIN4	PD7
	AIN5	PD6
	AIN6	PD5
one	AIN7	PD4
	AIN8	PE5
	AIN9	PE4
	C0+	PC6
	C0-	PC7
	C0o	PF0
	C1+	PC5
	C1-	PC4
	Clo	PF1
	C2+	PG6
	C2-	PG7
	C2o	PF2
	I2C0SCL	PB2
	I2C0SDA	PB3
	I2C4SCL	PG2
	I2C4SDA	PG3
	I2C5SCL	PG6
	I2C5SDA	PG7
	M0PWM0	PH0
	M0PWM1	PH1
 		+

Table 23-6. Possible Pin Assignments for Alternate Functions (continued)

	GPIO Function
M1FAULT3	PK3
M1PWM4	PF0
M1PWM5	PF1
M1PWM6	PF2
M1PWM7	PF3
SSI0Clk	PA2
SSI0Fss	PA3
SSIORX	PA4
SSIOTx	PA5
SSI2Rx	PH6
SSI2Tx	PH7
SWCLK	PC0
SWDIO	PC1
SWO	PC3
TOCCPO	PF0
T0CCP1	PF1
TCK	PC0
TDI	PC2
TDO	PC3
TMS	PC1
TRCLK	PF3
TRD0	PF2
TRD1	PF1
TRD2	PF0
TRD3	PF4
U0Rx	PA0
UOTx	PA1
U1DCD	PF2
U1DSR	PF3
U1DTR	PF4
UlRI	PE7
U3Rx	PC6
U3Tx	PC7
U5Tx	PE5
U6Rx	PD4
U6Tx	PD5
U7Rx	PE0
U7Tx	PE1
USB0DM	PJ0
USB0DP	PJ1
USB0ID	PB0
	M1PWM4 M1PWM5 M1PWM6 M1PWM7 SSIOC1k SSIOFSS SSIOTX SSIOTX SSI2TX SWCLK SWDIO SWO TOCCPO TOCCP1 TCK TDI TDO TMS TRCLK TRDO TRD1 TRD2 TRD3 UORX UOTX U1DCD U1DSR U1DTR U1DTR U1DTR U1DTR U1RI U3RX U3TX U6TX U7TX USBODM USBODP

Table 23-6. Possible Pin Assignments for Alternate Functions (continued)

# of Possible Assignments	Alternate Function	GPIO Function
	USB0VBUS	PB1

Table 23-6. Possible Pin Assignments for Alternate Functions (continued)

# of Possible Assignments	Alternate Function	GPIO Function
	CAN1Rx	PA0 PE6
	CAN1Tx	PA1 PE7
	I2C1SCL	PA6 PG4
	I2C1SDA	PA7 PG5
	I2C2SCL	PE4 PF6
	I2C2SDA	PE5 PF7
	I2C3SCL	PD0 PG0
	I2C3SDA	PD1 PG1
	M0FAULT3	PF5 PH3
	м0рwм2	PB4 PH2
	морwм3	PB5 PH3
	M1FAULT1	PG0 PK1
	M1FAULT2	PG1 PK2
	M1PWM0	PD0 PG2
	M1PWM1	PD1 PG3
	NMI	PD7 PF0
	SSI1Clk	PD0 PF2
	SSI1Fss	PD1 PF3
	SSI1Rx	PD2 PF0
	SSI1Tx	PD3 PF1
two	SSI2Clk	PB4 PH4
	SSI2Fss	PB5 PH5
	T2CCP1	PB1 PF5
	T3CCP0	PB2 PF6
	T3CCP1	PB3 PF7
	T4CCP0	PC0 PG0
	T4CCP1	PC1 PG1
	T5CCP0	PC2 PG2
	T5CCP1	PC3 PG3
	U1CTS	PC5 PF1
	Ulrts	PC4 PF0
	U1Rx	PB0 PC4
	U1Tx	PB1 PC5
	U2Rx	PD6 PG4
	U2Tx	PD7 PG5
	U4Rx	PC4 PJ0
	U4Tx	PC5 PJ1
	U5Rx	PE4 PJ2
	WT0CCP0	PC4 PG4
	WT0CCP1	PC5 PG5
-	WT1CCP0	PC6 PG6

Table 23-6. Possible Pin Assignments for Alternate Functions (continued)

WT1CCP1 PC7 PG7 WT2CCP0 PD0 PH0 WT2CCP1 PD1 PH1 WT3CCP0 PD2 PH4 WT3CCP1 PD3 PH5 WT4CCP0 PD4 PH6 WT4CCP1 PD5 PH7 WT5CCP0 PD6 PH2 WT5CCP1 PD7 PH3 CANORX PB4 PE4 PE CANOTX PB5 PE5 PE IDX1 PC4 PG5 PE M0FAULT2 PF4 PG3 PE M0PWM4 PE4 PG4 PE M0PWM5 PE5 PG5 PE	
WT2CCP1 PD1 PH1 WT3CCP0 PD2 PH4 WT3CCP1 PD3 PH5 WT4CCP0 PD4 PH6 WT4CCP1 PD5 PH7 WT5CCP0 PD6 PH2 WT5CCP1 PD7 PH3 CAN0Rx PB4 PE4 PI CAN0Tx PB5 PE5 PI IDX1 PC4 PG5 PI M0FAULT2 PF4 PG3 PI M0PWM4 PE4 PG4 PI M0PWM5 PE5 PG5 PI	
WT3CCP0 PD2 PH4 WT3CCP1 PD3 PH5 WT4CCP0 PD4 PH6 WT4CCP1 PD5 PH7 WT5CCP0 PD6 PH2 WT5CCP1 PD7 PH3 CAN0Rx PB4 PE4 PH CAN0Tx PB5 PE5 PH IDX1 PC4 PG5 PH M0FAULT2 PF4 PG3 PH M0PWM4 PE4 PG4 PH M0PWM5 PE5 PG5 PH	
WT3CCP1 PD3 PH5 WT4CCP0 PD4 PH6 WT4CCP1 PD5 PH7 WT5CCP0 PD6 PH2 WT5CCP1 PD7 PH3 CAN0Rx PB4 PE4 PI CAN0Tx PB5 PE5 PI IDX1 PC4 PG5 PI M0FAULT2 PF4 PG3 PI M0PWM4 PE4 PG4 PI M0PWM5 PE5 PG5 PI	
WT4CCP0 PD4 PH6 WT4CCP1 PD5 PH7 WT5CCP0 PD6 PH2 WT5CCP1 PD7 PH3 CAN0Rx PB4 PE4 PH CAN0Tx PB5 PE5 PH IDX1 PC4 PG5 PH M0FAULT2 PF4 PG3 PH M0PWM4 PE4 PG4 PH M0PWM5 PE5 PG5 PH	
WT4CCP1 PD5 PH7 WT5CCP0 PD6 PH2 WT5CCP1 PD7 PH3 CAN0Rx PB4 PE4 PH CAN0Tx PB5 PE5 PH IDX1 PC4 PG5 PH M0FAULT2 PF4 PG3 PH M0PWM4 PE4 PG4 PH M0PWM5 PE5 PG5 PH	
WT5CCP0 PD6 PH2 WT5CCP1 PD7 PH3 CAN0Rx PB4 PE4 PI CAN0Tx PB5 PE5 PI IDX1 PC4 PG5 PI M0FAULT2 PF4 PG3 PI M0PWM4 PE4 PG4 PI M0PWM5 PE5 PG5 PI	
WT5CCP1 PD7 PH3 CAN0RX PB4 PE4 PE CAN0TX PB5 PE5 PE IDX1 PC4 PG5 PE M0FAULT2 PF4 PG3 PE M0PWM4 PE4 PG4 PE M0PWM5 PE5 PG5 PE	
CANORX PB4 PE4 PI CANOTX PB5 PE5 PI IDX1 PC4 PG5 PI MOFAULT2 PF4 PG3 PI MOPWM4 PE4 PG4 PI MOPWM5 PE5 PG5 PI	
CANOTX PB5 PE5 PI IDX1 PC4 PG5 PI M0FAULT2 PF4 PG3 PI M0PWM4 PE4 PG4 PI M0PWM5 PE5 PG5 PI	
IDX1 PC4 PG5 PG M0FAULT2 PF4 PG3 PI M0PWM4 PE4 PG4 PI M0PWM5 PE5 PG5 PI	=0
M0FAULT2 PF4 PG3 PI M0PWM4 PE4 PG4 PI M0PWM5 PE5 PG5 PI	=3
M0PWM4 PE4 PG4 PI M0PWM5 PE5 PG5 PI	G 7
M0PWM5 PE5 PG5 PI	H2
	H4
251 257 25	H5
M1FAULTO PF4 PF7 Pk	(0
M1PWM2 PA6 PE4 PC	G4
M1PWM3 PA7 PE5 PC	3 5
PhA0 PD6 PF0 Pf	14
three PhA1 PC5 PG0 Pc	G3
PhB0 PD7 PF1 Pi	H5
PhB1 PC6 PG1 Pc	G4
SSI3Clk PD0 PH0 Pi	<0
SSI3Fss PD1 PH1 P	K1
SSI3RX PD2 PH2 PI	< 2
SSI3Tx PD3 PH3 P	K 3
T1CCP0 PB4 PF2 Po	JO
T1CCP1 PB5 PF3 Po	J1
T2CCP0 PB0 PF4 Po	J2
IDX0 PD3 PF4 PH1	PJ2
M0FAULT0 PD2 PD6 PF2	PH0
M0FAULT1 PD7 PF3 PG2	PH1
four M0PWM6 PC4 PD0 PG6	PH6
M0PWM7 PC5 PD1 PG7	PH7
USB0EPEN PC6 PD2 PF4	DC4
USB0PFLT PC7 PD3 PF5	F G 4

23.6 Connections for Unused Signals

Table 23-7 on page 1375 shows how to handle signals for functions that are not used in a particular system implementation for devices that are in a 100-pin LQFP package. Two options are shown in the table: an acceptable practice and a preferred practice for reduced power consumption and improved EMC characteristics. If a module is not used in a system, and its inputs are grounded, it

is important that the clock to the module is never enabled by setting the corresponding bit in the **RCGCx** register.

Table 23-7. Connections for Unused Signals (100-Pin LQFP)

Function	Signal Name	Pin Number	Acceptable Practice	Preferred Practice
GPIO	All unused GPIOs	-	NC	GND
	HIB	51	NC	NC
	VBAT	55	NC	VDD
Hibernate	WAKE	50	NC	GND
Преттате	XOSC0	52	NC	GND
	XOSC1	54	NC	NC
	GNDX	53	GND	GND
No Connects	NC	-	NC	NC
	OSC0	65	NC	GND
System Control	OSC1	66	NC	NC
	RST	63	Pull up as shown in Figure 5-1 on page 219	Connect through a capacitor to GND as close to pin as possible
USB	USB0DM	68	NC	GND
036	USB0DP	69	NC	GND

24 Electrical Characteristics

24.1 Operating Characteristics

Table 24-1. Temperature Characteristics

Characteristic	Symbol	Value	Unit
Case operating temperature range	T _C	-40 to +90	°C
Unpowered storage temperature range	T _S	-65 to +150	°C

Table 24-2. Thermal Characteristics^a

Characteristic	Symbol	Value	Unit
Thermal resistance (junction to board) ^b	ОЈВ	26.5	°C/W
Thermal resistance (junction to case) ^b	Θ _{JC}	8.9	°C/W
Junction to top of package	Ψ_{JT}	0.2	°C/W
Junction to board	Ψ_{JB}	26.1	°C/W
Junction temperature	T _J	$T_{B} + (P \cdot \Theta_{JB})^{c}$ $T_{C} + (P \cdot \Theta_{JC})^{d}$	°C
		$T_C + (P \cdot \Theta_{JC})^d$	

a. For more details about thermal metrics and definitions, see the Semiconductor and IC Package Thermal Metrics Application Report (literature number SPRA953).

Table 24-3. ESD Absolute Maximum Ratings

	Parameter	Min	Nom	Max	Unit
Component-Level ESD	V _{ESDHBM} b	-	-	2.0	kV
Stress Voltage ^a	V _{ESDCDM} ^c	-	-	500	V

a. Electrostatic discharge (ESD) to measure device sensitivity/immunity to damage caused by electrostatic discharges in device

- b. Level listed is passing level per ANSI/ESDA/JEDEC JS-001. JEDEC document JEP155 states that 500V HBM allows safe manufacturing with a standard ESD control process.
- c. Level listed is the passing level per EIA-JEDEC JESD22-C101E. JEDEC document JEP157 states that 250V CDM allows safe manufacturing with a standard ESD control process.

b. Junction to board thermal resistance (Θ_{JB}) and junction to case thermal resistance (Θ_{JC}) numbers are determined by a package simulator.

c. T_B is temperature of the board.

d. This equation may give a junction temperature estimate that is higher than the actual junction temperature. Please see the Semiconductor and IC Package Thermal Metrics Application Report (literature number SPRA953)

24.2 Maximum Ratings

The maximum ratings are the limits to which the device can be subjected without permanently damaging the device. Device reliability may be adversely affected by exposure to absolute-maximum ratings for extended periods.

Note: The device is not guaranteed to operate properly at the maximum ratings.

Table 24-4. Maximum Ratings

Parameter	Parameter Name ^a	V	Unit	
Parameter	Farameter Name	Min	Max	Unit
V_{DD}	V _{DD} supply voltage	0	4	V
V_{DDA}	V _{DDA} supply voltage ^b	0	4	V
V_{BAT}	V _{BAT} battery supply voltage	0	4	V
V _{IN_GPIO}	Input voltage on GPIOs, regardless of whether the microcontroller is powered ^{cd}	-0.3	5.5	V
	Input voltage for PJ0, PJ1, PB0 and PB1 when configured as GPIO	-0.3	V _{DD} + 0.3	V
I _{GPIOMAX}	Maximum current per output pin	-	25	mA

a. Voltages are measured with respect to GND.

Important: This device contains circuitry to protect the I/Os against damage due to high-static voltages; however, it is advised that normal precautions be taken to avoid application of any voltage higher than maximum-rated voltages to this high-impedance circuit. Reliability of operation is enhanced if unused inputs are connected to an appropriate logic voltage level (see "Connections for Unused Signals" on page 1374).

b. To ensure proper operation, VDDA must be powered before VDD if sourced from different supplies, or connected to the same supply as VDD. Note that the minimum operating voltage for VDD differs from the minimum operating voltage for VDDA. This change should be accounted for in the system design if both are sourced from the same supply. There is not a restriction on order for powering off.

c. Applies to static and dynamic signals including overshoot.

d. Refer to Figure 24-16 on page 1401 for a representation of the ESD protection on GPIOs.

24.3 Recommended Operating Conditions

For special high-current applications, the GPIO output buffers may be used with the following restrictions. With the GPIO pins configured as 8-mA output drivers, a total of four GPIO outputs may be used to sink current loads up to 18 mA each. At 18-mA sink current loading, the V_{OL} value is specified as 1.2 V. The high-current GPIO package pins must be selected such that there are only a maximum of two per side of the physical package with the total number of high-current GPIO outputs not exceeding four for the entire package.

Table 24-5. Recommended DC Operating Conditions

Parameter	Parameter Name	Min	Nom	Max	Unit
V _{DD}	V _{DD} supply voltage	3.15	3.3	3.63	V
V_{DDA}	V _{DDA} supply voltage	2.97	3.3	3.63	V
V_{DDC}	V _{DDC} supply voltage	1.08	1.2	1.32	V
V _{DDCDS} ab	V _{DDC} supply voltage, Deep-sleep mode	1.08	-	1.32	V

a. These values are valid when LDO is in operation.

Table 24-6. Recommended GPIO Pad Operating Conditions

Parameter	Parameter Name	Min	Nom	Max	Unit
V _{IH}	GPIO high-level input voltage	0.65 * V _{DD}	-	5.5	V
V _{IL}	GPIO low-level input voltage	0	-	0.35 * V _{DD}	V
V _{HYS}	GPIO input hysteresis	0.2	-	-	V
V _{OH}	GPIO high-level output voltage	2.4	-	-	V
V _{OL}	GPIO low-level output voltage	-	-	0.4	V
	High-level source current, V _{OH} =2.4 V ^a		,		
1	2-mA Drive	2.0	-	-	mA
I _{OH}	4-mA Drive	4.0	-	-	mA
	8-mA Drive	8.0	-	-	mA
	Low-level sink current, V _{OL} =0.4 V ^a				
	2-mA Drive	2.0	-	-	mA
I _{OL}	4-mA Drive	4.0	-	-	mA
	8-mA Drive	8.0	-	-	mA
	8-mA Drive, V _{OL} =1.2 V	18.0	-	-	mA

a. I_O specifications reflect the maximum current where the corresponding output voltage meets the V_{OH}/V_{OL} thresholds. I_O current can exceed these limits (subject to absolute maximum ratings).

Table 24-7. GPIO Current Restrictions^a

Parameter	Parameter Name	Min	Nom	Max	Unit
I _{MAXL}	Cumulative maximum GPIO current per side, left ^b	-	-	70	mA
I _{MAXB}	Cumulative maximum GPIO current per side, bottom ^b	-	-	70	mA
I _{MAXR}	Cumulative maximum GPIO current per side, right ^b	-	-	75	mA
I _{MAXT}	Cumulative maximum GPIO current per side, top ^b	-	-	70	mA

a. Based on design simulations, not tested in production.

b. There are peripheral timing restrictions for SSI and LPC in Deep-sleep mode. Please refer to those peripheral characteristic sections for more information.

b. Sum of sink and source current for GPIOs as shown in Table 24-8 on page 1379.


Table 24-8. GPIO Package Side Assignments

Side	GPIOs
Left	PC[4-7], PD[0-3], PE[0-3], PH[0-3], PJ[2-3]
Bottom	PA[0-7], PF[0-5], PK[0-3]
Right	PB[0-3], PF7, PG[0-5], PJ[0-1]
Тор	PB[4-5], PC[0-3], PD[4-7], PE[4-7], PG[6-7], PH[4-7]

24.4 Load Conditions

Unless otherwise specified, the following conditions are true for all timing measurements.

Figure 24-1. Load Conditions




24.5 JTAG and Boundary Scan

Table 24-9. JTAG Characteristics

Parameter No.	Parameter	Parameter Name	Min	Nom	Max	Unit
J1	F _{TCK}	TCK operational clock frequency ^a	0 -			MHz
J2	T _{TCK}	TCK operational clock period	-	-	ns	
J3	T _{TCK_LOW}	TCK clock Low time	-	t _{TCK} /2	-	ns
J4	T _{TCK_HIGH}	TCK clock High time	-	t _{TCK} /2	-	ns
J5	T _{TCK_R}	TCK rise time	0	-	10	ns
J6	T _{TCK_F}	TCK fall time	0	-	10	ns
J7	T _{TMS_SU}	TMS setup time to TCK rise	8	-	-	ns
J8	T _{TMS_HLD}	TMS hold time from TCK rise	4	-	-	ns
J9	T _{TDI_SU}	TDI setup time to TCK rise	18	-	-	ns
J10	T _{TDI_HLD}	TDI hold time from TCK rise	4	-	-	ns
		TCK fall to Data Valid from High-Z, 2-mA drive		13	35	ns
		TCK fall to Data Valid from High-Z, 4-mA drive		9	26	ns
J11	T_{TDO_ZDV}	TCK fall to Data Valid from High-Z, 8-mA drive	-	8	26	ns
		${\tt TCK}$ fall to Data Valid from High-Z, 8-mA drive with slew rate control		10	29	ns
		TCK fall to Data Valid from Data Valid, 2-mA drive		14	20	ns
		TCK fall to Data Valid from Data Valid, 4-mA drive		10	26	ns
J12	T_{TDO_DV}	TCK fall to Data Valid from Data Valid, 8-mA drive	-	8	21	ns
		TCK fall to Data Valid from Data Valid, 8-mA drive with slew rate control		10	26	ns
		TCK fall to High-Z from Data Valid, 2-mA drive		7	16	ns
		TCK fall to High-Z from Data Valid, 4-mA drive		7	16	ns
J13	T_{TDO_DVZ}	TCK fall to High-Z from Data Valid, 8-mA drive	-	7	16	ns
		TCK fall to High-Z from Data Valid, 8-mA drive with slew rate control		8	19	ns

a. A ratio of at least 8:1 must be kept between the system clock and $\ensuremath{\mathtt{TCK}}.$

Figure 24-2. JTAG Test Clock Input Timing






Figure 24-3. JTAG Test Access Port (TAP) Timing

1382 February 20, 2013

24.6 Power and Brown-Out

Table 24-10. Power-On and Brown-Out Levels

Parameter No.	Parameter	Parameter Name	Min	Nom	Max	Unit
P1	T_{VDDA_RISE}	Analog Supply Voltage (VDDA) Rise Time	-	-	∞	μs
P2	T _{VDD_RISE}	I/O Supply Voltage (VDD) Rise Time	-	-	∞	μs
P3	T _{VDDC_RISE} ^a	Core Supply Voltage (VDDC) Rise Time	12.50	-	50.00	μs
P4	V _{POR}	Power-On Reset Threshold	2.00	2.30	2.60	V
P5	V	VDDA Power-OK Threshold (Rising Edge)	2.70	2.85	3.00	V
5	V_{VDDA_POK}	VDDA Power-OK Threshold (Falling Edge)	2.71	2.80	2.89	V
P6	V	VDD Power-OK Threshold (Rising Edge)	2.85	3.00	3.15	V
F0	V_{VDD_POK}	VDD Power-OK Threshold (Falling Edge)	2.70	2.78	2.87	V
P7	V _{VDD_BOR0}	Brown-Out 0 Reset Threshold	2.93	3.02	3.11	V
P8	V _{VDD_BOR1}	Brown-Out 1 Reset Threshold	2.83	2.92	3.01	V
P9	V	VDDC Power-OK Threshold (Rising Edge)	0.80	0.95	1.10	V
ΓÐ	V _{VDDC_POK}	VDDC Power-OK Threshold (Falling Edge)	0.71	0.80	0.89	V

a. The MIN and MAX value is based on an external filter capacitor load within the range of CLDO. Please refer to "On-Chip Low Drop-Out (LDO) Regulator" on page 1390 for the CLDO value.

24.6.1 VDDA Levels

The V_{DDA} supply has two monitors:

- Power-On Reset (POR)
- Power-OK (POK)

The POR monitor is used to keep the analog circuitry in reset until the V_{DDA} supply has reached the correct range for the analog circuitry to begin operating. The POK monitor is used to keep the digital circuitry in reset until the V_{DDA} power supply is at an acceptable operational level. The digital Power-On Reset ($\overline{\texttt{Digital POR}}$) is only released when the Power-On Reset has de-asserted and all of the Power-OK monitors for each of the supplies indicate that power levels are in operational ranges.

Once the V_{DDA} POK monitor has released the digital Power-On Reset on the initial power-up, voltage drops on the V_{DDA} supply will only be reflected in the following bits. The digital Power-On Reset will not be re-asserted.

- VDDARIS bit in the Raw Interrupt Status (RIS) register (see page 245).
- VDDAMIS bit in the Masked Interrupt Status and Clear (MISC) register (see page 250). This bit is set only if the VDDAIM bit in the Interrupt Mask Control (IMC) register has been set.

Figure 24-4 on page 1384 shows the relationship between V_{DDA}, POR, POK, and an interrupt event.




Figure 24-4. Power Assertions versus VDDA Levels

24.6.2 VDD Levels

The V_{DD} supply has three monitors:

- Power-OK (POK)
- Brown-Out Reset0 (BOR0)
- Brown-Out Reset1 (BOR1)

The POK monitor is used to keep the digital circuitry in reset until the V_{DD} power supply is at an acceptable operational level. The digital Power-On Reset ($\overline{\texttt{Digital POR}}$) is only released when the Power-On Reset has de-asserted and all of the Power-OK monitors for each of the supplies indicate that power levels are in operational ranges. The BOR0 and the BOR1 monitors are used to generate a reset to the device or assert an interrupt if the V_{DD} supply drops below its operational range. The BOR1 monitor's threshold is in between the BOR0 and POK thresholds.

If either a BOR0 event or a BOR1 event occurs, the following bits are affected:

- BORORIS or BORIRIS bits in the Raw Interrupt Status (RIS) register (see page 245).
- BOR0MIS or BOR1MIS bits in the **Masked Interrupt Status and Clear (MISC)** register (see page 250). These bits are set only if the respective BOR0IM or BOR1IM bits in the **Interrupt Mask Control (IMC)** register have been set.
- BOR bit in the **Reset Cause (RESC)** register (see page 253). This bit is set only if either of the BOR0 or BOR1 events have been configured to initiate a reset.

In addition, the following bits control both the BOR0 and BOR1 events:


■ BOROIM or BOR1IM bits in the Interrupt Mask Control (IMC) register (see page 248).

■ BOR0 or BOR1 bits in the **Power-On and Brown-Out Reset Control (PBORCTL)** register (see page 244).

Figure 24-5 on page 1385 shows the relationship between:

- lacksquare V_{DD} , POK, and a BOR0 event
- V_{DD}, POK, and a BOR1 event


Figure 24-5. Power and Brown-Out Assertions versus VDD Levels



24.6.3 VDDC Levels

The V_{DDC} supply has one monitor: the Power-OK (POK). The POK monitor is used to keep the digital circuitry in reset until the V_{DDC} power supply is at an acceptable operational level. The digital Power-On Reset (Digital POR) is only released when the Power-On Reset has de-asserted and all of the Power-OK monitors for each of the supplies indicate that power levels are in operational ranges. Figure 24-6 on page 1386 shows the relationship between POK and V_{DDC} .


Figure 24-6. POK assertion vs VDDC



24.6.4 VDD Glitches

Figure 24-7 on page 1386 shows the response of the BOR0, BOR1, and the POR circuit to glitches on the V_{DD} supply.

Figure 24-7. POR-BOR0-BOR1 VDD Glitch Response



24.6.5 VDD Droop Response

Figure 24-8 on page 1387 shows the response of the BOR0, BOR1, and the POR monitors to a drop on the V_{DD} supply.




Figure 24-8. POR-BOR0-BOR1 VDD Droop Response

February 20, 2013 1387


24.7 Reset

Table 24-11. Reset Characteristics

Parameter No.	Parameter	Parameter Name	Min	Nom	Max	Unit
R1	T _{DPORDLY}	Digital POR to Internal Reset assertion delay ^a	0.80	-	5.35	μs
R2	T _{IRTOUT}	Internal Reset timeout	-	-	500	μs
R3	T _{BOR0DLY}	BOR0 to Internal Reset assertion delay ^a	0.25	-	1.95	μs
R3	T _{BOR1DLY}	BOR1 to Internal Reset assertion delay ^a	0.75	-	5.95	μs
R4	T _{RSTMIN}	Minimum RST pulse width	-	250	-	ns
R5	T _{IRHWDLY}	RST to Internal Reset assertion delay	-	250	-	ns
R6	T _{IRSWR}	Internal reset timeout after software-initiated system reset	-	2.07	-	μs
R7	T _{IRWDR}	Internal reset timeout after Watchdog reset	-	2.10	-	μs
R8	T _{IRMFR}	Internal reset timeout after MOSC failure reset	-	1.92	-	μs

a. Timing values are dependent on the $\ensuremath{V_{DD}}$ power-down ramp rate.

Figure 24-9. Digital Power-On Reset Timing



The digital Power-On Reset is only released when the analog Power-On Reset has de-asserted and all of the Power-OK monitors for each of the supplies indicate that power levels are in operational ranges.

Figure 24-10. Brown-Out Reset Timing




Figure 24-11. External Reset Timing (RST)




Figure 24-12. Software Reset Timing




Figure 24-13. Watchdog Reset Timing





Figure 24-14. MOSC Failure Reset Timing



24.8 On-Chip Low Drop-Out (LDO) Regulator

Table 24-12. LDO Regulator Characteristics

Parameter	Parameter Name	Min	Nom	Max	Unit
C _{LDO}	External filter capacitor size for internal power supply ^a	2.5	-	4.0	μF
ESR	Filter capacitor equivalent series resistance	10	-	100	mΩ
ESL	Filter capacitor equivalent series inductance	-	-	0.5	nH
V _{LDO}	LDO output voltage	1.08	1.2	1.32	V
I _{INRUSH}	Inrush current	50	-	250	mA

a. The capacitor should be connected as close as possible to pin 86.

24.9 Clocks

The following sections provide specifications on the various clock sources and mode.

24.9.1 PLL Specifications

The following tables provide specifications for using the PLL.

Table 24-13. Phase Locked Loop (PLL) Characteristics

Parameter	Parameter Name	Min	Nom	Max	Unit
F _{REF_XTAL}	Crystal reference	5 ^a	-	25	MHz
F _{REF_EXT}	External clock reference ^a	5 ^a	-	25	MHz
F _{PLL}	PLL frequency ^b	-	400	-	MHz
	PLL lock time, enabling the PLL	-	-	512 * (N+1) ^c	reference clocks ^d
T _{READY}	PLL lock time, changing the XTAL field in the RCC/RCC2 register or changing the OSCSRC between MOSC and PIOSC		-	128 * (N+1) ^c	reference clocks ^d

a. If the PLL is not used, the minimum input frequency can be 4 MHz.

Table 24-14 on page 1391 shows the actual frequency of the PLL based on the crystal frequency used (defined by the XTAL field in the **RCC** register).

Table 24-14. Actual PLL Frequency

XTAL	Crystal Frequency (MHz)	MINT	MFRAC	Q	N	PLL Multiplier	PLL Frequency (MHz)	Error
0x09	5.0	0x50	0x0	0x0	0x0	80	400	-
0x0A	5.12	0x9C	0x100	0x0	0x1	156.25	400	- 1
0x0B	6.0	0xC8	0x0	0x0	0x2	200	400	-
0x0C	6.144	0xC3	0x140	0x0	0x2	195.3125	400	-
0x0D	7.3728	0xA2	0x30A	0x0	0x2	162.7598	399.9984	0.0004%
0x0E	8.0	0x32	0x0	0x0	0x0	50	400	-
0x0F	8.192	0xC3	0x140	0x0	0x3	195.3125	400	-
0x10	10.0	0x50	0x0	0x0	0x1	80	400	-
0x11	12.0	0xC8	0x0	0x0	0x5	200	400	-
0x12	12.288	0xC3	0x140	0x0	0x5	195.3125	400	-
0x13	13.56	0xB0	0x3F6	0x0	0x5	176.9902	399.9979	0.0005%
0x14	14.318	0xC3	0x238	0x0	0x6	195.5547	399.9982	0.0005%
0x15	16.0	0x32	0x0	0x0	0x1	50	400	-
0x16	16.384	0xC3	0x140	0x0	0x7	195.3125	400	-
0x17	18	0xC8	0x0	0x0	0x8	200	400	-
0x18	20	0x50	0x0	0x0	0x3	80	400	-
0x19	24	0x32	0x0	0x0	0x2	50	400	-

b. PLL frequency is automatically calculated by the hardware based on the XTAL field of the RCC register. The PLL frequency that is set by the hardware can be calculated using the values in the PLLFREQ1 and PLLFREQ1 registers.

c. N is the value in the ${\tt N}$ field in the PLLFREQ1 register.

d. A reference clock is the clock period of the crystal being used, which can be MOSC or PIOSC. For example, a 16-MHz crystal connected to MOSC yields a reference clock of 62.5 ns.

Table 24-14. Actual PLL Frequency (continued)

XTAL	Crystal Frequency (MHz)	MINT	MFRAC	Q	N	PLL Multiplier	PLL Frequency (MHz)	Error
0x1A	25	0x50	0x0	0x0	0x4	80	400	-

24.9.2 PIOSC Specifications

Table 24-15. PIOSC Clock Characteristics

Parameter	Parameter Name	Min	Nom	Max	Unit
F _{PIOS}	Internal 16-MHz precision oscillator frequency variance (factory calibrated at 25 °C C and 3.3 V) across the specified voltage and temperature range	-	-	±3%	-

a. This parameter value remains valid if recalibration occurs.

24.9.3 Low-Frequency Internal Oscillator (LFIOSC) Specifications

Table 24-16. Low-Frequency internal Oscillator Characteristics

Parameter	Parameter Name	Min	Nom	Max	Unit
F _{LFIOSC}	Low-frequency internal oscillator (LFIOSC) frequency	10	33	90	KHz

24.9.4 Hibernation Clock Source Specifications

Table 24-17. Hibernation Oscillator Input Characteristics

Parameter	Parameter Name	Min	Nom	Max	Unit
F _{HIBLFIOSC}	Hibernation low frequency internal oscillator (HIB LFIOSC) frequency	10	33	90	KHz
C ₁ , C ₂	External load capacitance on XOSC0, XOSC1 pins ^a	12	-	24	pF
C _{PKG}	Device package stray shunt capacitance ^a	-	0.5	-	pF
C _{PCB}	PCB stray shunt capacitance ^a	-	0.5	-	pF
C ₀	Crystal shunt capacitance ^a	-	3	-	pF
C _{SHUNT}	Total shunt capacitance ^a	-	-	4	pF
ESR	Crystal effective series resistance, OSCDRV = 0 ^b	-	-	50	kΩ
ESK	Crystal effective series resistance, OSCDRV = 1 ^b	-	-	75	kΩ
DL	Oscillator output drive level	-	-	0.25	μW
T _{START}	Oscillator startup time, when using a crystal ^c	-	600	1500 ^d	ms
V _{IH} ^e	CMOS input high level, when using an external oscillator with Supply > 3.3 V	2.64	-	-	V
V IH	CMOS input high level, when using an external oscillator with 1.8 V ≤ Supply ≤ 3.3 V	0.8 * Supply	-	-	V
V _{IL} e	CMOS input low level, when using an external oscillator with 1.8 V ≤ Supply ≤ 3.63 V	-	-	0.2 * Supply	V
V _{HYS} e	CMOS input buffer hysteresis, when using an external oscillator with 1.8 V ≤ Supply ≤ 3.63 V	360	960	1390	mV
DC _{HIBOSC_EXT}	External clock reference duty cycle	30	-	70	%

a. See information below table.

b. Crystal ESR specified by crystal manufacturer.

- c. Oscillator startup time is specified from the time the oscillator is enabled to when it reaches a stable point of oscillation such that the internal clock is valid.
- d. Only valid for recommended supply conditions. Measured with OSCDRV bit set (high drive strength enabled, 24 pF).
- e. Specification is relative to the larger of V_{DD} or V_{BAT} .

The load capacitors added on the board, C_1 and C_2 , should be chosen such that the following equation is satisfied (see Table 24-17 on page 1392 for typical values).

- C_I = load capacitance specified by crystal manufacturer
- $C_L = (C_1 C_2)/(C_1 + C_2) + C_{PKG} + C_{PCB}$
- C_{SHUNT} = C_{PKG} + C_{PCB} + C₀ (total shunt capacitance seen across XOSC0, XOSC1)
- lacksquare C_{PKG} , C_{PCB} as measured across the XOSC0, XOSC1 pins excluding the crystal
- Clear the OSCDRV bit in the Hibernation Control (HIBCTL) register for $C_{1,2} \le 18$ pF; set the OSCDRV bit for $C_{1,2} > 18$ pF.
- C₀ = Shunt capacitance of crystal specified by the crystal manufacturer

24.9.5 Main Oscillator Specifications

Table 24-18. Main Oscillator Input Characteristics

Parameter	Parameter Name	Min	Nom	Max	Unit
F _{MOSC}	Parallel resonance frequency	4 ^a	-	25	MHz
C ₁ , C ₂	External load capacitance on OSC0, OSC1 pinsb	12	-	24	pF
C _{PKG}	Device package stray shunt capacitance ^b	-	0.5	-	pF
C _{PCB}	PCB stray shunt capacitance ^b	-	0.5	-	pF
C ₀	Crystal shunt capacitance ^{bc}	-	4	-	pF
C _{SHUNT}	Total shunt capacitance ^b	-	-	4	pF
	Crystal effective series resistance, 4 MHz ^{dc}	-	-	300	Ω
	Crystal effective series resistance, 6 MHz ^{dc}	-	-	200	Ω
ESR	Crystal effective series resistance, 8 MHz ^{dc}	-	-	130	Ω
ESK	Crystal effective series resistance, 12 MHz ^{dc}	-	-	120	Ω
	Crystal effective series resistance, 16 MHz ^{dc}	-	-	100	Ω
	Crystal effective series resistance, 25 MHz ^{dc}	-	-	50	Ω
DL	Oscillator output drive level ^e	-	OSC _{PWR}	-	mW
T _{START}	Oscillator startup time, when using a crystal ^f	-	-	18	ms
V _{IH}	CMOS input high level, when using an external oscillator	0.65 * V _{DD}	-	V _{DD}	V
V _{IL}	CMOS input low level, when using an external oscillator	GND	-	0.35 * V _{DD}	V
V _{HYS}	CMOS input buffer hysteresis, when using an external oscillator	150	-	-	mV
DC _{OSC_EXT}	External clock reference duty cycle	45	-	55	%

a. 5 MHz is the minimum when using the PLL.

b. See information below table.

c. Crystal vendors can be contacted to confirm these specifications are met for a specific crystal part number if the vendors generic crystal datasheet show limits outside of these specifications.

- d. Crystal ESR specified by crystal manufacturer.
- e. $OSC_{PWR} = (2 * pi * F_P * C_L * 2.5)^2 * ESR / 2$. An estimation of the typical power delivered to the crystal is based on the C_L , F_P and ESR parameters of the crystal in the circuit as calculated by the OSC_{PWR} equation. Ensure that the value calculated for OSC_{PWR} does not exceed the crystal's drive-level maximum.
- f. Oscillator startup time is specified from the time the oscillator is enabled to when it reaches a stable point of oscillation such that the internal clock is valid.

The load capacitors added on the board, C_1 and C_2 , should be chosen such that the following equation is satisfied (see Table 24-18 on page 1393 for typical values and Table 24-19 on page 1394 for detailed crystal parameter information).

- C_I = load capacitance specified by crystal manufacturer
- $C_L = (C_1 C_2)/(C_1 + C_2) + C_{SHUNT}$
- C_{SHUNT} = C₀ + C_{PKG} + C_{PCB} (total shunt capacitance seen across OSC0, OSC1 crystal inputs)
- C_{PKG}, C_{PCB} = the mutual caps as measured across the OSC0,OSC1 pins excluding the crystal.
- C₀ = Shunt capacitance of crystal specified by the crystal manufacturer

Table 24-19 on page 1394 lists part numbers of crystals that have been simulated and confirmed to operate within the specifications in Table 24-18 on page 1393. Other crystals that have nearly identical crystal parameters can be expected to work as well.

In the table below, the crystal parameters labeled C0, C1 and L1 are values that are obtained from the crystal manufacturer. These numbers are usually a result of testing a relevant batch of crystals on a network analyzer. The parameters labeled ESR, DL and C_L are maximum numbers usually available in the data sheet for a crystal.

The table also includes three columns of Recommended Component Values. These values apply to system board components. C_1 and C_2 are the values in pico Farads of the load capacitors that should be put on each leg of the crystal pins to ensure oscillation at the correct frequency. Rs is the value in $k\Omega$ of a resistor that is placed in series with the crystal between the OSC1 pin and the crystal pin. Rs dissipates some of the power so the Max DI crystal parameter is not exceeded. Only use the recommended C_1 , C_2 , and Rs values with the associated crystal part. The values in the table were used in the simulation to ensure crystal startup and to determine the worst case drive level (WC DI). The value in the WC DI column should not be greater than the Max DI Crystal parameter. The WC DI value can be used to determine if a crystal with similar parameter values but a lower Max DI value is acceptable.

Table 24-19. Crystal Parameters

					ပ္မ	Crystal Para Typical Values		,			Co	omme mpon Values	ent	(
MFG	MFG Part#	Holder	PKG Size (mm x mm)	Freq (MHz)	Crystal Spec	C0 (pF)	C1 (FF)	L1 (mH)	ESR (Ω)	Мах DI (µW)	C _L (pf)	C ₁ (pF)	C ₂ (pF)	Rs (kΩ)	WC DI (µW)
NDK	NX8045GB- 4.000M-STD- CJL-5	NX8045GB	8 x 4.5	4	STD-CJL-5	1.00	2.70	598.10	300	500	8	12	12	0	132
FOX	FQ1045A-4	2-SMD	10 x 4.5	4	FQ1045A	1.18	4.05	396.00	150	500	10	14	14	0	103

Table 24-19. Crystal Parameters (continued)

							Cr	stal Par	amete	rs		Reco	omme	nded	
					0	Ту	pical V	alues	Ма	x Valu	es		mpon Value:		
MFG	MFG Part#	Holder	PKG Size (mm x mm)	Freq (MHz)	Crystal Spec	C0 (pF)	C1 (fF)	L1 (mH)	ESR (Ω)	Max DI (µW)	C _L (pf)	C ₁ (pF)	C ₂ (pF)	Rs (kΩ)	WC DI (µW)
NDK	NX8045GB- 5.000M-STD- CSF-4	NX8045GB	8 x 4.5	5	STD-CJL-4	1.00	2.80	356.50	250	500	8	12	12	0	164
NDK	NX8045GB- 6.000M-STD- CSF-4	NX8045GB	8 x 4.5	6	STD-CJL-4	1.30	4.10	173.20	250	500	8	12	12	0	214
FOX	FQ1045A-6	2-SMD	10 x 4.5	6	FQ1045A	1.37	6.26	112.30	150	500	10	14	14	0	209
NDK	NX8045GB- 8.000M-STD- CSF-6	NX8045GB	8 x 4.5	8	STD-CSF-6	1.00	2.80	139.30	200	500	8	12	12	0	277
FOX	FQ7050B-8	4-SMD	7 x 5	8	FQ7050	1.95	6.69	59.10	80	500	10	14	14	0	217
ECS	ECS-80-16-28A-TR	HC49/US	12.5 x 4.85	8	CSM-4A	1.82	4.90	85.70	80	500	16	24	24	0	298
NDK	NX3225GA- 12.000MHZ- STD-CRG-2	NX3225GA	3.2 x 2.5	12	STD-CRG-2	0.70	2.20	81.00	100	200	8	12	12	2.5	147
NDK	NX5032GA- 12.000MHZ- LN-CD-1	NX5032GA	5 x 3.2	12	LN-CD-1	0.93	3.12	56.40	120	500	8	12	12	0	362
FOX	FQ5032B-12	4-SMD	5 x 3.2	12	FQ5032	1.16	4.16	42.30	80	500	10	14	14	0	370
NDK	NX3225GA- 16.000MHZ- STD-CRG-2	NX3225GA	3.2 x 2.5	16	STD-CRG-2	1.00	2.90	33.90	80	200	8	12	12	2	188
NDK	NX5032GA- 16.000MHZ- LN-CD-1	NX5032GA	5 x 3.2	16	LN-CD-1	1.02	3.82	25.90	120	500	8	10	10	0	437
ECS	ECS-160-942-CKM-TR	ECX-42	4 x 2.5	16	ECX-42	1.47	3.90	25.84	60	300	9	12	12	0.5	289
NDK	NX3225GA- 25.000MHZ- STD-CRG-2	NX3225GA	3.2 x 2.5	25	STD-CRG-2	1.10	4.70	8.70	50	200	8	12	12	2	181
AURIS	Q-25.000M- HC3225/4- F-30-30-E-12-TR	HC3225/4	3.2 x 2.5	25	HC3225	1.58	5.01	8.34	50	500	12	16	16	1	331
FOX	FQ5032B-25	4-SMD	5 x 3.2	25	FQ5032	1.69	7.92	5.13	50	500	10	14	14	0.5	433

Table 24-20. Supported MOSC Crystal Frequencies^a

Value	Crystal Frequency (MHz) Not Using the PLL	Crystal Frequency (MHz) Using the PLL
0x00-0x5	rese	rved

Table 24-20. Supported MOSC Crystal Frequencies (continued)

Value	Crystal Frequency (MHz) Not Using the PLL	Crystal Frequency (MHz) Using the PLL
0x06	4 MHz	reserved
0x07	4.096 MHz	reserved
0x08	4.9152 MHz	reserved
0x09	5 MHz	(USB)
0x0A	5.12	MHz
0x0B	6 MHz	(USB)
0x0C	6.144	MHz
0x0D	7.3728	8 MHz
0x0E	8 MHz	(USB)
0x0F	8.192	. MHz
0x10	10.0 MH	Iz (USB)
0x11	12.0 MH	Iz (USB)
0x12	12.288	8 MHz
0x13	13.56	MHz
0x14	14.318	18 MHz
0x15	16.0 MHz (reso	et value)(USB)
0x16	16.384	4 MHz
0x17	18.0 MH	Iz (USB)
0x18	20.0 MH	Iz (USB)
0x19	24.0 MH	Iz (USB)
0x1A	25.0 MH	Iz (USB)

a. Frequencies that may be used with the USB interface are indicated in the table.

24.9.6 System Clock Specification with ADC Operation

Table 24-21. System Clock Characteristics with ADC Operation

Parameter	Parameter Name	Min	Nom	Max	Unit
Sysauc	System clock frequency when the ADC module is operating (when PLL is bypassed). ^a	15.9952	16	16.0048	MHz

a. Clock frequency (plus jitter) must be stable inside specified range. ADC can be clocked from the PLL, directly from an external clock source, or from the PIOSC, as long as frequency absolute precision is inside specified range.

24.9.7 System Clock Specification with USB Operation

Table 24-22. System Clock Characteristics with USB Operation

Parameter	Parameter Name	Min	Nom	Max	Unit
F _{sysusb}	System clock frequency when the USB module is operating (note that MOSC must be the clock source, either with or without using the PLL)	20	-	-	MHz

24.10 Sleep Modes

Table 24-23. Sleep Modes AC Characteristics^a

Parameter No	Parameter	Parameter Name	Min	Nom	Max	Unit
D1	T _{WAKE_S}	Time to wake from interrupt in sleep mode ^b	-	-	2	system clocks
	т	Time to wake from interrupt in deep-sleep mode, using PIOSC for both Run mode and Deep-sleep mode ^{b c}	-	1.25	-	μs
	I WAKE_DS	Time to wake from interrupt in deep-sleep mode, using PIOSC for Run mode and LFIOSC for Deep-sleep mode ^{b c}	-	350	-	μs
D2	T _{WAKE_PLL_DS}	Time to wake from interrupt in deep-sleep mode when using the PLL ^b	-	-	T _{READY}	ms

a. Values in this table assume the LFIOSC is the clock source during sleep or deep-sleep mode.

b. Specified from registering the interrupt to first instruction.

c. If the main oscillator is used for run mode, add the main oscillator startup time, T_{START} .

24.11 Hibernation Module

The Hibernation module requires special system implementation considerations because it is intended to power down all other sections of its host device, refer to "Hibernation Module" on page 491.

Table 24-24. Hibernation Module Battery Characteristics


Parameter	Parameter Name	Min	Nominal	Max	Unit
V _{BAT}	Battery supply voltage	1.8	3.0	3.6 ^a	V
	Low battery detect voltage, VBATSEL=0x0	1.8	1.9	2.0	V
V	Low battery detect voltage, VBATSEL=0x1	2.0	2.1	2.2	V
V _{LOWBAT}	Low battery detect voltage, VBATSEL=0x2	2.2	2.3	2.4	V
	Low battery detect voltage, VBATSEL=0x3	2.4	2.5	2.6	V

a. To ensure proper functionality, any voltage input within the range of 3.6 V < VBAT ≤ 4 V must be connected through a diode.

Table 24-25. Hibernation Module AC Characteristics

Parameter No	Parameter	Parameter Name	Min	Nom	Max	Unit
H1	T _{WAKE}	WAKE assertion time	100	-	-	ns
H2	T _{WAKE_TO_HIB}	WAKE assert to HIB desassert (wake up time)	-	-	1	hibernation clock period
H3	T_{VDD_RAMP}	V _{DD} ramp to 3.0 V	-	Depends on characteristics of power supply	-	μѕ
H4	T _{VDD_CODE}	V _{DD} at 3.0 V to internal POR deassert; first instruction executes	-	-	500	μs

Figure 24-15. Hibernation Module Timing



24.12 Flash Memory and EEPROM

Table 24-26. Flash Memory Characteristics

Parameter	Parameter Name	Min	Nom	Max	Unit
PE _{CYC}	Number of guaranteed program/erase cycles before failure ^a	100,000	-	-	cycles
T _{RET}	Data retention, -40°C to +85°C	20	-	-	years
T _{PROG64}	Program time for double-word-aligned 64 bits of data ^b	30	50	300	μs
т	Page erase time, <1k cycles	2	25	-	ms
T _{ERASE}	Page erase time, 100k cycles	-	-	900	ms
т	Mass erase time, <1k cycles	70	200	-	ms
T _{ME}	Mass erase time, 100k cycles	-	-	900	ms

a. A program/erase cycle is defined as switching the bits from 1-> 0 -> 1.

Table 24-27, EEPROM Characteristics^a

Parameter	Parameter Name	Min	Nom	Max	Unit
EPE _{CYC} ^b	Number of guaranteed mass program/erase cycles of a single word before failure ^c	500,000	-	-	cycles
ET _{RET}	Data retention, -40°C to +85°C	20	-	-	years
	Program time for 32 bits of data - space available	-	110	600	μs
ET _{PROG}	Program time for 32 bits of data - requires a copy to the copy buffer, copy buffer has space and less than 10% of EEPROM used		30	-	ms
	Program time for 32 bits of data - requires a copy to the copy buffer, copy buffer has space and greater than 90% of EEPROM used	-	-	900	ms
	Program time for 32 bits of data - requires a copy to the copy buffer, copy buffer requires an erase and less than 10% of EEPROM used	-	60	-	ms
	Program time for 32 bits of data - requires a copy to the copy buffer, copy buffer requires an erase and greater than 90% of EEPROM used		-	1800	ms
ET _{READ}	Read access time	-	4	-	system clocks
ET _{ME}	Mass erase time, <1k cycles	70	200	-	ms
	Mass erase time, 100k cycles	-	-	900	ms

a. Because the EEPROM operates as a background task and does not prevent the CPU from executing from Flash memory, the operation will complete within the maximum time specified provided the EEPROM operation is not stalled by a Flash memory program or erase operation.

b. If programming fewer than 64 bits of data, the programming time is the same. For example, if only 32 bits of data need to be programmed, the other 32 bits are masked off.

b. One word can be written more than 500K times, but these writes impact the endurance of the words in the meta-block that the word is within. Different words can be written such that any or all words can be written more than 500K times when write counts per word stay about the same. See the section called "Endurance" on page 536 for more information.

c. A program/erase cycle is defined as switching the bits from 1-> 0 -> 1.

24.13 Input/Output Pin Characteristics

24.13.1 GPIO Module Characteristics

Note: All GPIO signals are 5-V tolerant when configured as inputs except for PJO, PJI, PBO and PBI, which are limited to 3.6 V. See "Signal Description" on page 646 for more information

on GPIO configuration.

Note: GPIO pads are tolerant to 5-V digital inputs without creating reliability issues, as long as the supply voltage, VDD, is present. There are limitations to how long a 5-V input can be present on any given I/O pad if VDD is not present. Not meeting these conditions will affect reliability of the device and affect the GPIO characteristics specifications.

- If the voltage applied to a GPIO pad is in the high voltage range (5V +/- 10%) while VDD is not present, such condition should be allowed for a maximum of 10,000 hours at 27°C or 5,000 hours at 85°C, over the lifetime of the device.
- If the voltage applied to a GPIO pad is in the normal voltage range (3.3V +/- 10%) while VDD is not present or if the voltage applied is in the high voltage range (5V +/- 10%) while VDD is present, there are no constraints on the lifetime of the device.

Table 24-28. GPIO Module Characteristics^a

Parameter	Parameter Name	Min	Nom	Max	Unit
R _{GPIOPU}	GPIO internal pull-up resistor	13	20	30	kΩ
R _{GPIOPD}	GPIO internal pull-down resistor	13	20	35	kΩ
I _{LKG+}	GPIO input leakage current, $0 \text{ V} \leq \text{V}_{IN} \leq \text{V}_{DD}$ GPIO pins ^b	-	-	1.0	μА
	GPIO input leakage current, 0 V < $V_{IN} \le V_{DD}$, GPIO pins configured as ADC or analog comparator inputs	-	-	2.0	μА
	GPIO rise time, 2-mA drive ^c	-	14.2	16.1	ns
_	GPIO rise time, 4-mA drive ^c		11.9	15.5	ns
T _{GPIOR}	GPIO rise time, 8-mA drive ^c		8.1	11.2	ns
	GPIO rise time, 8-mA drive with slew rate control ^c		9.5	11.8	ns
	GPIO fall time, 2-mA drive ^d		25.2	29.4	ns
T _{GPIOF}	GPIO fall time, 4-mA drive ^d	-	13.3	16.8	ns
	GPIO fall time, 8-mA drive ^d		8.6	11.2	ns
	GPIO fall time, 8-mA drive with slew rate control ^d		11.3	12.9	ns

a. V_{DD} must be within the range specified in Table 24-5 on page 1378.

24.13.2 Types of I/O Pins and ESD Protection

With respect to ESD and leakage current, three types of I/O pins exist on the device: Power I/O pins, I/O pins with fail-safe ESD protection (GPIOs and XOSCn pins) and I/O pins with non-fail-safe ESD protection (any non-power, non-GPIO, non-XOSCn pins). This section covers I/O pins with fail-safe ESD protection and I/O pins with non-fail-safe ESD protection. Power I/O pin voltage and current limitations are specified in "Recommended Operating Conditions" on page 1378.

b. The leakage current is measured with V_{IN} applied to the corresponding pin(s). The leakage of digital port pins is measured individually. The port pin is configured as an input and the pullup/pulldown resistor is disabled.

c. Time measured from 20% to 80% of $\ensuremath{V_{DD}}.$

d. Time measured from 80% to 20% of $\ensuremath{V_{DD}}.$

24.13.2.1 Fail-Safe Pins

GPIOs, pins for the Hibernate 32-kHz oscillator (XOSCn), Hibernate input pins, and I/O pins for the USB PHY use ESD protection as shown in Figure 24-16 on page 1401.

An unpowered device cannot be parasitically powered through any of these pins. This ESD protection prevents a direct path between these I/O pads and any power supply rails in the device. GPIO/XOSCn pad input voltages should be kept inside the maximum ratings specified in Table 24-4 on page 1377 to ensure current leakage and current injections are within acceptable range. Current leakages and current injection for these pins are specified in Table 24-28 on page 1400.

Figure 24-16 on page 1401 shows a diagram of the ESD protection on fail-safe pins.

Figure 24-16. ESD Protection on Fail-Safe Pins




Table 24-29. Pad Voltage/Current Characteristics for Fail-Safe Pins^a

Parameter	Parameter Name	Min	Nom	Max	Unit
I _{LKG+}	GPIO input leakage current, V _{DD} < V _{IN} ≤ 4.5 V ^{bb}	-	-	700	μΑ
	GPIO input leakage current, 4.5 V < V _{IN} ≤ 5.5 V ^{bc}	-	-	100	μΑ
I _{LKG} -	GPIO input leakage current, V _{IN} < -0.3 V ^{bd}	-	-	_e	μΑ
	GPIO input leakage current, -0.3 V ≤ V _{IN} < 0 V ^b	-	-	10	μΑ
I _{INJ+}	DC injection current, V _{DD} < V _{IN} ≤ 5.5 V ^{fg}	-	-	I _{LKG+}	μΑ
I _{INJ-}	DC injection current, V _{IN} ≤ 0 V ^g	-	-	0.5	mA

- a. VIN must be within the range specified in Table 24-4 on page 1377.
- b. To protect internal circuitry from over-voltage, the GPIOs have an internal voltage clamp that limits internal swings to V_{DD} without affecting swing at the I/O pad. This internal clamp starts turning on while $V_{DD} < V_{IN} < 4.5$ V and causes a somewhat larger (but bounded) current draw. To save power, static input voltages between V_{DD} and 4.5 V should be avoided.
- c. Leakage current above maximum voltage (V_{IN} = 5.5V) is not guaranteed, this condition is not allowed and can result in permanent damage to the device.
- d. Leakage outside the minimum range (-0.3V) is unbounded and must be limited to IINJ- using an external resistor.
- e. In this case, $I_{\text{LKG-}}$ is unbounded and must be limited to $I_{\text{INJ-}}$ using an external resistor.
- f. Current injection is internally bounded for GPIOs, and maximum current into the pin is given by ILKG+ for $V_{DD} < V_{IN} < 5.5$ V.
- g. If the I/O pad is not voltage limited, it should be current limited (to IINJ+ and IINJ-) if there is any possibility of the pad voltage exceeding the VIO limits (including transient behavior during supply ramp up, or at any time when the part is unpowered).

24.13.2.2 Non-Fail-Safe Pins

The ADC external voltage reference input pins and the Main Oscillator (MOSC) crystal connection pins have ESD protection as shown in Figure 24-17 on page 1402. These pins have a potential path between the I/O pad and an internal power rail if either one of the ESD diodes is accidentally forward biased. The voltage and current of these pins should follow the specifications in Table 24-30 on page 1402 to prevent potential damage to the device. In addition to the specifications outlined in Table 24-30 on page 1402, it is recommended that the ADC external reference specifications in

Figure 24-17 on page 1402 shows a diagram of the ESD protection on non-fail-safe pins.

Table 24-31 on page 1403 be adhered to in order to prevent any gain error.






Table 24-30. Non-Fail-Safe I/O Pad Voltage/Current Characteristics abcd

Parameter	Parameter Name	Min	Nom	Max	Unit
V _{IO}	IO pad voltage limits	-0.3	V_{DD}	V _{DD} +0.3	V
I _{LKG+}	Positive IO leakage for V _{IO} Max ^{ef}	-	-	10	μΑ
I _{LKG-}	Negative IO leakage for V _{IO} Min ^{ef}	-	-	10	μΑ
I _{INJ+}	Max positive injection ⁹	-	-	2	mA
I _{INJ-}	Max negative injection if not voltage protected ⁹	-	-	-0.5	mA

a. V_{IN} must be within the range specified in Table 24-4 on page 1377. Leakage current outside of this maximum voltage is not guaranteed and can result in permanent damage of the device.

- d. I/O pads should be protected if at any point the IO voltage has a possibility of going outside the limits shown in the table. If the part is unpowered, the IO pad Voltage or Current must be limited (as shown in this table) to avoid powering the part through the IO pad, causing potential irreversible damage.
- e. This value applies to an I/O pin that is voltage-protected within the Min and Max V_{IO} ratings. Leakage outside the specified voltage range is unbounded and must be limited to I_{INJ} using an external resistor.
- f. MIN and MAX leakage current for the case when the I/O is voltage-protected to VIO Min or VIO Max.
- g. If an I/O pin is not voltage-limited, it should be current-limited (to I_{INJ+} and I_{INJ-}) if there is any possibility of the pad voltage exceeding the V_{IO} limits (including transient behavior during supply ramp up, or at any time when the part is unpowered).

b. VDD must be within the range specified in Table 24-5 on page 1378.

c. To avoid potential damage to the part, either the voltage or current on the ESD-protected, non-Power, non-Hibernate/XOSC input/outputs should be limited externally as shown in this table.

24.14 Analog-to-Digital Converter (ADC)

Table 24-31. ADC Electrical Characteristics^{ab}

Parameter	Parameter Name	Min	Nom	Max	Unit
POWER SUPF	PLY REQUIREMENTS				
V_{DDA}	ADC supply voltage	2.97	3.3	3.63	V
GNDA	ADC ground voltage	-	0	-	V
VDDA / GNDA	VOLTAGE REFERENCE				
C _{REF}	Voltage reference decoupling capacitance	-	1.0 // 0.01 ^c	-	μF
EXTERNAL VO	OLTAGE REFERENCE INPUT				•
V _{REFA+}	Positive external voltage reference for ADC, when \mbox{VREF} field in the ADCCTL register is not $0x0^d$ -	2.4	V _{DDA}	V_{DDA}	V
$V_{REFA ext{-}}$	Negative external voltage reference for ADC, when VREF field in the ADCCTL register is not $0x0^d$	GNDA	GNDA	0.3	V
I _{VREF}	Current on VREF+ input, using external V _{REF+} = 3.3 V	-	330.5	440	μA
I _{LVREF}	DC leakage current on VREF+ input when external VREF disabled	-	-	2.0	μA
C _{REF}	External reference decoupling capacitance ^d	-	1.0 // 0.01 ^e	-	μF
ANALOG INPL	JT				
	Single-ended, full- scale analog input voltage, internal reference ^{fg}	0	-	V_{DDA}	V
V	Differential, full-scale analog input voltage, internal reference ^{fh}	-V _{DDA}	-	V_{VDDA}	V
V _{ADCIN}	Single-ended, full-scale analog input voltage, external reference ^{dg}	V _{REFA-}	-	V _{REFA+}	V
	Differential, full-scale analog input voltage, external reference ^{di}	- (V _{REFA+} - V _{REFA-})	-	V _{REFA+} - V _{REFA-}	V
VIN _{CM}	Input common mode voltage, differential mode	-	-	(VREFP + VREFN) / 2	mV
	, k			± 25	
l _L	ADC input leakage current ^k	-	-	2.0	μA
R _{ADC}	ADC equivalent input resistance ^k	-	-	2.5	kΩ
C _{ADC}	ADC equivalent input capacitance ^k	-	-	10	pF
R _S	Analog source resistance ^k	-	-	500	Ω
SAMPLING DY				Г	
F _{ADC}	ADC conversion clock frequency	-	16	-	MHz
F _{CONV}	ADC conversion rate		1	T	MSPS
T _S	ADC sample time	-	250	-	ns
T _C	ADC conversion time ^m		1		μs
T _{LT}	Latency from trigger to start of conversion	-	2	-	ADC clocks
SYSTEM PER	FORMANCE when using external reference ^{no}				
N	Resolution		12		bits
INL	Integral nonlinearity error, over full input range	-	±1.5	±3.0	LSB

Table 24-31. ADC Electrical Characteristics (continued)

Parameter	Parameter Name	Min	Nom	Max	Unit
DNL	Differential nonlinearity error, over full input range	-	±0.8	+2.0/-1.0 ^p	LSB
Eo	Offset error	-	±1.0	±3.0	LSB
E _G	Gain error ^q	-	±2.0	±3.0	LSB
E _T	Total unadjusted error, over full input range ^r	-	±2.5	±4.0	LSB
SYSTEM PER	FORMANCE when using internal reference		,		
N	Resolution		12		bits
INL	Integral nonlinearity error, over full input range	-	±1.5	±3.0	LSB
DNL	Differential nonlinearity error, over full input range	-	±0.8	±1.0	LSB
Eo	Offset error	-	±5.0	±15.0	LSB
E _G	Gain error ^q	-	±10.0	±30.0	LSB
E _T	Total unadjusted error, over full input range ^r	-	±10.0	±30.0	LSB
DYNAMIC CH	ARACTERISTICS				
SNR _D	Signal-to-noise-ratio, Differential input, V _{ADCIN} : -20dB FS, 1KHz ^u	70	72	-	dB
SDR _D	Signal-to-distortion ratio, Differential input, V _{ADCIN} : -3dB FS, 1KHz ^{uvw}	72	75	-	dB
SNDR _D	Signal-to-Noise+Distortion ratio, Differential input, V _{ADCIN} : -3dB FS, 1KHz ^{uxy}	68	70	-	dB
SNR _S	Signal-to-noise-ratio, Single-ended input, V _{ADCIN} : -20dB FS, 1KHz	60	65	-	dB
SDR _S	Signal-to-distortion ratio, Single-ended input, V _{ADCIN} : -3dB FS, 1KHz ^{vw}	70	72	-	dB
SNDR _S	Signal-to-Noise+Distortion ratio, Single-ended input, V _{ADCIN} : -3dB FS, 1KHz ^{Xyz}	60	63	-	dB
TEMPERATUR	RE SENSOR				
V _{TSENS}	Temperature sensor voltage, junction temperature 25 °C	-	1.633	-	V
S _{TSENS}	Temperature sensor slope, ambient temperature -40 °C to 85 °C	-	-13.3	-	mV/°C
E _{TSENS}	Temperature sensor accuracy, ambient temperature -40 °C to 85 °C aa	-	-	±5	°C

a. At junction temperature= -40 $^{\circ}$ C to 85 $^{\circ}$ C, V_{REF+}= 3.3V, F_{ADC}=16 MHz unless otherwise noted.

b. Best design practices suggest that static or quiet digital I/O signals be configured adjacent to sensitive analog inputs to reduce capacitive coupling and cross talk. Analog signals configured adjacent to ADC input channels should meet the same source resistance and bandwidth limitations that apply to the ADC input signals.

c. Two capacitors in parallel

d. Assumes external filtering network between VREFA+ and VREFA- as shown in Figure 24-18 on page 1405. External reference noise level must be under 12bit (-74 dB) of Full Scale input, over input bandwidth, measured at VREFA+ - VREFA+.

e. Two capacitors in parallel.


f. Internal reference is connected directly between V_{DDA} and GNDA (VREFi = V_{DDA} - GNDA). In this mode, E_O, E_G, E_T, and dynamic specifications are adversely affected due to internal voltage drop and noise on V_{DDA} and GNDA. Internal reference voltage is selected when VREF field in the **ADCCTL** register is 0x0.

g. $V_{ADCIN} = V_{INP} - V_{INN}$

h. With signal common mode as $V_{DDA}/2$.

- i. With signal common mode as (V_{REF+} + V_{REF-}/2.
- j. This parameter is defined as the average of the differential inputs.
- k. As shown in Figure 24-19 on page 1406, R_{ADC} is the total equivalent resistance in the input line all the way up to the sampling node at the input of the ADC.
- I. See "System Clock Specification with ADC Operation" on page 1396 for full ADC clock frequency specification.
- m. ADC conversion time (Tc) includes the ADC sample time (Ts).
- n. Low noise environment is assumed in order to obtain values close to spec. Board must have good ground isolation between analog and digital grounds, a clean reference voltage is assumed, and input signal must be bandlimited to Nyquist bandwidth. No anti-aliasing filter is provided internally.
- o. ADC static measurements taken by averaging over several samples. At least 20-sample averaging is assumed to obtain expected typical or maximum spec values.
- p. 12-bit DNL
- q. Gain error is measured at max code after compensating for offset. Gain error is equivalent to "Full Scale Error." It can be given in % of slope error, or in LSB, as done here.
- r. Total Unadjusted Error is the maximum error at any one code versus the ideal ADC curve. It includes all other errors (offset error, gain error and INL) at any given ADC code.
- s. A low-noise environment is assumed in order to obtain values close to spec. The board must have good ground isolation between analog and digital grounds and a clean reference voltage. The input signal must be band-limited to Nyquist bandwidth. No anti-aliasing filter is provided internally.
- t. ADC dynamic characteristics are measured using low-noise board design, with low-noise reference voltage (< -74dB noise level in signal BW) and low-noise analog supply voltage. Board noise and ground bouncing couple into the ADC and affect dynamic characteristics. Clean external reference must be used to achieve shown specs.</p>
- u. Differential signal with correct common mode, applied between two ADC inputs.
- v. SDR = -THD in dB.
- w. For higher frequency inputs, degradation in SDR should be expected.
- x. SNDR = S/(N+D) = SINAD (in dB)
- y. Effective number of bits (ENOB) can be calculated from SNDR: ENOB = (SNDR 1.76) / 6.02.
- z. Single-ended inputs are more sensitive to board and trace noise than differential inputs; SNR and SNDR measurements on single-ended inputs are highly dependent on how clean the test set-up is. If the input signal is not well-isolated on the board, higher noise than specified could potentially be seen at the ADC output.
- aa. Note that this parameter does not include ADC error.

Figure 24-18. ADC External Reference Filtering



Stellaris® Microcontroller Input PAD Equivalent Circuit Z_{ADC} ESD clamps to GND only $\mathsf{R}_{\mathsf{ADC}}$ 12-bit SAR ADC Converter 5V ESD Clamp 12-bit Word $\mathsf{R}_{\mathsf{ADC}}$ Input PAD Equivalent Pin **-**VVV Circuit $\mathsf{R}_{\mathsf{ADC}}$ Input PAD . Equivalent Circuit

Figure 24-19. ADC Input Equivalency Diagram


24.15 Synchronous Serial Interface (SSI)

Table 24-32, SSI Characteristics

Parameter No.	Parameter	Parameter Name	Min	Nom	Мах	Unit
S1	т	SSIClk cycle time, as master ^a	40	-	-	ns
51	T _{CLK_PER}	SSIC1k cycle time, as slave ^b	150	-	-	ns
S2	Т	ssiclk high time, as master	20	-	-	ns
32	T _{CLK_HIGH}	SSIClk high time, as slave	75	-	-	ns
S3	т	ssiclk low time, as master	20	-	-	ns
33	T _{CLK_LOW}	SSIC1k low time, as slave	75	-	-	ns
S4	T _{CLKR}	ssiclk rise time ^c	1.25	-	-	ns
S5	T _{CLKF}	ssiclk fall time ^c	1.25	-	-	ns
S6	T _{DMD}	Data from master valid delay time	0	-	T _{SYSCLK}	ns
S7	T _{DMS}	Data from master setup time, as master in Tx mode	9.1	-	-	ns
S8	T _{DMH}	Data from master hold time, as master in Tx mode	0.3	-	-	ns
S9	T _{DMS}	Data to master setup time, as master in Rx mode	2.8	-	0.5*T _{CLK_PER} - 17.1	ns
S10	T _{DMH}	Data to master hold time, as master in Rx mode	15.97	-	0.5*T _{CLK_PER} - 4.0	ns
S11	T _{DSS}	Data from slave setup time, as slave in Tx mode	0.1666*T _{CLK_PER} - 27.7	-	-	ns
S12	T _{DSH}	Data from slave hold time, as slave in Tx mode	0.333* _{TCLK_PER} + 5.5	-	-	ns
S13	T _{DSS}	Data to slave setup time, as slave in Rx mode	0.1666* _{TCLK_PER} - 2.96	-	-	ns
S14	T _{DSH}	Data to slave hold time, as slave in Rx mode	0.333* _{TCLK_PER} - 0.73	-	-	ns

a. In master mode, the system clock must be at least twice as fast as the SSICIk.

Figure 24-20. SSI Timing for TI Frame Format (FRF=01), Single Transfer Timing Measurement



b. In slave mode, the system clock must be at least 6 times faster than the SSICIk.

c. Note that the delays shown are using 8-mA drive strength.

Figure 24-21. SSI Timing for MICROWIRE Frame Format (FRF=10), Single Transfer





Figure 24-22. SSI Timing for SPI Frame Format (FRF=00), with SPH=1



1408 February 20, 2013


24.16 Inter-Integrated Circuit (I²C) Interface

Table 24-33. I²C Characteristics

Parameter No.	Parameter	Parameter Name	Min	Nom	Max	Unit
I1 ^a	T _{SCH}	Start condition hold time	36	-	-	system clocks
I2 ^a	T _{LP}	Clock Low period	36	-	-	system clocks
I3 ^b	T _{SRT}	I2CSCL/I2CSDA rise time (V $_{IL}$ =0.5 V to V $_{IH}$ =2.4 V)	-	-	(see note b)	ns
I4 ^a	T _{DH}	Data hold time	2	-	-	system clocks
15 ^c	T _{SFT}	<code>I2CSCL/I2CSDA</code> fall time (V $_{IH}$ =2.4 V to V $_{IL}$ =0.5 V)	-	9	10	ns
I6 ^a	T _{HT}	Clock High time	24	-	-	system clocks
I7 ^a	T _{DS}	Data setup time	18	-	-	system clocks
I8 ^a	T _{SCSR}	Start condition setup time (for repeated start condition only)	36	-	-	system clocks
19 ^a	T _{SCS}	Stop condition setup time	24	-	-	system clocks

a. Values depend on the value programmed into the TPR bit in the I²C Master Timer Period (I2CMTPR) register; a TPR programmed for the maximum I2CSCL frequency (TPR=0x2) results in a minimum output timing as shown in the table above. The I²C interface is designed to scale the actual data transition time to move it to the middle of the I2CSCL Low period. The actual position is affected by the value programmed into the TPR; however, the numbers given in the above values are minimum values.

Figure 24-23. I²C Timing



b. Because I2CSCL and I2CSDA operate as open-drain-type signals, which the controller can only actively drive Low, the time I2CSCL or I2CSDA takes to reach a high level depends on external signal capacitance and pull-up resistor values.

c. Specified at a nominal 50 pF load.

24.17 Universal Serial Bus (USB) Controller

The Stellaris[®] USB controller electrical specifications are compliant with the *Universal Serial Bus Specification Rev. 2.0* (full-speed and low-speed support) and the *On-The-Go Supplement to the USB 2.0 Specification Rev. 1.0*. Some components of the USB system are integrated within the LM4F232H5QC microcontroller and specific to the Stellaris microcontroller design.

24.18 Analog Comparator

Table 24-34. Analog Comparator Characteristics ab

Parameter	Parameter Name	Min	Nom	Max	Unit
V _{INP} ,V _{INN}	Input voltage range		-	V_{DDA}	V
V _{CM}	Input common mode voltage range	GNDA	-	V_{DDA}	V
V _{OS}	Input offset voltage	-	±10	±50 ^d	mV
I _{INP} ,I _{INN}	Input leakage current over full voltage range	-	-	2.0	μA
C _{MRR}	Common mode rejection ratio	-	50	-	dB
T _{RT}	Response time	-	-	1.0 ^e	μs
T _{MC}	Comparator mode change to Output Valid	-	-	10	μs

a. Best design practices suggest that static or quiet digital I/O signals be configured adjacent to sensitive analog inputs to reduce capacitive coupling and cross talk.

Table 24-35. Analog Comparator Voltage Reference Characteristics

Parameter	Parameter Name	Min	Nom	Max	Unit
R _{HR}	Resolution in high range	-	V _{DDA} /29.4	-	V
R _{LR}	Resolution in low range	-	V _{DDA} /22.12	-	V
A _{HR}	Absolute accuracy high range	-	-	±R _{HR} /2	V
A _{LR}	Absolute accuracy low range	-	-	±R _{LR} /2	V

Table 24-36. Analog Comparator Voltage Reference Characteristics, V_{DDA} = 3.3V, EN= 1, and RNG = 0

VREF Value	V _{IREF} Min	Ideal V _{IREF}	V _{IREF} Max	Unit
0x0	0.731	0.786	0.841	V
0x1	0.843	0.898	0.953	V
0x2	0.955	1.010	1.065	V
0x3	1.067	1.122	1.178	V
0x4	1.180	1.235	1.290	V
0x5	1.292	1.347	1.402	V
0x6	1.404	1.459	1.514	V
0x7	1.516	1.571	1.627	V
0x8	1.629	1.684	1.739	V
0x9	1.741	1.796	1.851	V
0xA	1.853	1.908	1.963	V
0xB	1.965	2.020	2.076	V
0xC	2.078	2.133	2.188	V

b. To achieve best analog results, the source resistance driving the analog inputs, V_{INP} and V_{INN} , should be kept low.

c. The external voltage inputs to the Analog Comparator are designed to be highly sensitive and can be affected by external noise on the board. For this reason, $V_{\rm INP}$ and $V_{\rm INN}$ must be set to different voltage levels during idle states to ensure the analog comparator triggers are not enabled. If an internal voltage reference is used, it should be set to a mid-supply level. When operating in Sleep/Deep-Sleep modes, the Analog Comparator module external voltage inputs set to different levels (greater than the input offset voltage) to achieve minimum current draw.

d. Measured at VREF=100 mV.

e. Measured at external VREF=100 mV, input signal switching from 75 mV to 125 mV.

Table 24-36. Analog Comparator Voltage Reference Characteristics, V_{DDA} = 3.3V, EN= 1, and RNG = 0 (continued)

VREF Value	V _{IREF} Min	Ideal V _{IREF}	V _{IREF} Max	Unit
0xD	2.190	2.245	2.300	V
0xE	2.302	2.357	2.412	V
0xF	2.414	2.469	2.525	V

Table 24-37. Analog Comparator Voltage Reference Characteristics, V_{DDA} = 3.3V, EN= 1, and RNG = 1

VREF Value	V _{IREF} Min	Ideal V _{IREF}	V _{IREF} Max	Unit
0x0	0.000	0.000	0.074	V
0x1	0.076	0.149	0.223	V
0x2	0.225	0.298	0.372	V
0x3	0.374	0.448	0.521	V
0x4	0.523	0.597	0.670	V
0x5	0.672	0.746	0.820	V
0x6	0.822	0.895	0.969	V
0x7	0.971	1.044	1.118	V
0x8	1.120	1.193	1.267	V
0x9	1.269	1.343	1.416	V
0xA	1.418	1.492	1.565	V
0xB	1.567	1.641	1.715	V
0xC	1.717	1.790	1.864	V
0xD	1.866	1.939	2.013	V
0xE	2.015	2.089	2.162	V
0xF	2.164	2.238	2.311	V

24.19 Current Consumption

24.19.1 Preliminary Current Consumption

The following table provides preliminary figures for current consumption while ongoing characterization is completed.

Table 24-38. Preliminary Current Consumption

Parameter	Parameter Name	Conditions	Nom	Max	Unit
	Run mode 1 (Flash loop)	V _{DD} = 3.3 V	50	-	mA
		V _{DDA} = 3.3 V			
		Peripherals = All ON			
		System Clock = 80 MHz (with PLL)			
		Temp = 25°C			
	Run mode 1 (SRAM loop)	V _{DD} = 3.3 V	40	-	mA
		V _{DDA} = 3.3 V			
		Peripherals = All ON			
		System Clock = 80 MHz (with PLL)			
,		Temp = 25°C			
I _{DD_RUN}	Run mode 2 (Flash loop)	V _{DD} = 3.3 V	30	-	mA
		V _{DDA} = 3.3 V			
		Peripherals = All OFF			
		System Clock = 80 MHz (with PLL)			
		Temp = 25°C			
	Run mode 2 (SRAM loop)	V _{DD} = 3.3 V	20	-	mA
		V _{DDA} = 3.3 V			
		Peripherals = All OFF			
		System Clock = 80 MHz (with PLL)			
		Temp = 25°C			
I _{DDA_RUN} a	Run mode	V _{DD} = 3.6 V	-	4.5	mA
		V _{DDA} = 3.6 V			
		Peripherals = All ON			
		System Clock = 80 MHz (with PLL)			
		Temp = 25°C			

Table 24-38. Preliminary Current Consumption (continued)

Parameter	Parameter Name	Conditions	Nom	Max	Unit
		V _{DD} = 3.3 V	12	-	mA
		V _{DDA} = 3.3 V			
		Peripherals = All OFF			
		System Clock = 80 MHz (with PLL)			
		Temp = 25°C			
		V _{DD} = 3.3 V	4.5	-	mA
		V _{DDA} = 3.3 V			
I _{DD_SLEEP}	Sleep mode	Peripherals = All OFF			
	·	System Clock =16 MHz (with PIOSC) ^b			
		Temp = 25°C			
		V _{DD} = 3.3 V	3.8	-	mA
		V _{DDA} = 3.3 V			
		Peripherals = All OFF			
		System Clock =1 MHz (with PIOSC/16) ^b			
		Temp = 25°C			
Ind Deepsleep	Deep-sleep mode	V _{DD} = 3.3 V	1.05	- 1	mA
DD_DEE! OLLE!		V _{DDA} = 3.3 V			
		Peripherals = All OFF			
		System Clock = LFIOSC			
		Temp = 25°C			
I _{HIB_NORTC}	Hibernate mode (external	V _{BAT} = 3.0 V	1.6	-	μΑ
	wake, RTC disabled)	$V_{DD} = 0 V$			
		V _{DDA} = 0 V			
		System Clock = OFF			
		Hibernate Module = 32.768 kHz			
I _{HIB_RTC}	Hibernate mode (RTC	V _{BAT} = 3.0 V	1.7	-	μΑ
_	enabled)	$V_{DD} = 0 V$			
		V _{DDA} = 0 V			
		System Clock = OFF			
		Hibernate Module = 32.768 kHz			
I _{HIB_VDD3ON}	Hibernate mode	V _{BAT} = 3.0 V	5.0	- 1	μΑ
2200.1	(VDD3ON mode)	V _{DD} = 3.3 V			
		V _{DDA} = 3.3 V			
		System Clock = OFF			
	I .	l -		1 1	

a. The value for I_{DDA_RUN} is included in the above values for I_{DD_RUN} .

b. Note that if the MOSC is the source of the Run-mode system clock and is powered down in Sleep mode, wake time is increased by T_{MOSC_SETTLE}.

A Ordering and Contact Information

A.1 Ordering Information




Table A-1. Part Ordering Information

Orderable Part Number	Description
LM4F232H5QCFIG	Stellaris® LM4F232H5QC Microcontroller Industrial Temperature 100-pin LQFP
LM4F232H5QCFIGR	Stellaris LM4F232H5QC Microcontroller Industrial Temperature 100-pin LQFP Tape-and-reel

A.2 Part Markings

The Stellaris microcontrollers are marked with an identifying number. This code contains the following information:

- The first and second lines indicate the part number, for example, LM4F232H5QDFIGA0. The second letter in the part number indicates the product status. An M indicates the part is fully qualified and released to production. An X, for example, LX4F232H5QDFIGA0, indicates the part is experimental and requires a waiver.
- The third line contains internal tracking numbers.

A.3 Kits

The Stellaris Family provides the hardware and software tools that engineers need to begin development quickly.

- Reference Design Kits accelerate product development by providing ready-to-run hardware and comprehensive documentation including hardware design files
- Evaluation Kits provide a low-cost and effective means of evaluating Stellaris microcontrollers before purchase

■ Development Kits provide you with all the tools you need to develop and prototype embedded applications right out of the box

See the website at www.ti.com/stellaris for the latest tools available, or ask your distributor.

A.4 Support Information

For support on Stellaris products, contact the TI Worldwide Product Information Center nearest you.

B Package Information

B.1 100-Pin LQFP Package

B.1.1 Package Dimensions

Figure B-1. Stellaris[®] LM4F232H5QC 100-Pin LQFP Package Dimensions

MTQF013A - OCTOBER 1994 - REVISED DECEMBER 1996 PZ (S-PQFP-G100) PLASTIC QUAD FLATPACK 0,50 0,08 (M) 75 100 0,13 NOM Gage Plane 12,00 TYP 14,20 13,80 0,25 16,20 0,05 MIN SQ 15,80 1,45 0,75 1,35 0,45 **Seating Plane** 1,60 MAX 0,08 4040149/B 11/96

NOTES: A. All linear dimensions are in millimeters.

- B. This drawing is subject to change without notice.
- C. Falls within JEDEC MS-026

IMPORTANT NOTICE

Texas Instruments Incorporated and its subsidiaries (TI) reserve the right to make corrections, enhancements, improvements and other changes to its semiconductor products and services per JESD46, latest issue, and to discontinue any product or service per JESD48, latest issue. Buyers should obtain the latest relevant information before placing orders and should verify that such information is current and complete. All semiconductor products (also referred to herein as "components") are sold subject to TI's terms and conditions of sale supplied at the time of order acknowledgment.

TI warrants performance of its components to the specifications applicable at the time of sale, in accordance with the warranty in TI's terms and conditions of sale of semiconductor products. Testing and other quality control techniques are used to the extent TI deems necessary to support this warranty. Except where mandated by applicable law, testing of all parameters of each component is not necessarily performed.

TI assumes no liability for applications assistance or the design of Buyers' products. Buyers are responsible for their products and applications using TI components. To minimize the risks associated with Buyers' products and applications, Buyers should provide adequate design and operating safeguards.

TI does not warrant or represent that any license, either express or implied, is granted under any patent right, copyright, mask work right, or other intellectual property right relating to any combination, machine, or process in which TI components or services are used. Information published by TI regarding third-party products or services does not constitute a license to use such products or services or a warranty or endorsement thereof. Use of such information may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

Reproduction of significant portions of TI information in TI data books or data sheets is permissible only if reproduction is without alteration and is accompanied by all associated warranties, conditions, limitations, and notices. TI is not responsible or liable for such altered documentation. Information of third parties may be subject to additional restrictions.

Resale of TI components or services with statements different from or beyond the parameters stated by TI for that component or service voids all express and any implied warranties for the associated TI component or service and is an unfair and deceptive business practice. TI is not responsible or liable for any such statements.

Buyer acknowledges and agrees that it is solely responsible for compliance with all legal, regulatory and safety-related requirements concerning its products, and any use of TI components in its applications, notwithstanding any applications-related information or support that may be provided by TI. Buyer represents and agrees that it has all the necessary expertise to create and implement safeguards which anticipate dangerous consequences of failures, monitor failures and their consequences, lessen the likelihood of failures that might cause harm and take appropriate remedial actions. Buyer will fully indemnify TI and its representatives against any damages arising out of the use of any TI components in safety-critical applications.

In some cases, TI components may be promoted specifically to facilitate safety-related applications. With such components, TI's goal is to help enable customers to design and create their own end-product solutions that meet applicable functional safety standards and requirements. Nonetheless, such components are subject to these terms.

No TI components are authorized for use in FDA Class III (or similar life-critical medical equipment) unless authorized officers of the parties have executed a special agreement specifically governing such use.

Only those TI components which TI has specifically designated as military grade or "enhanced plastic" are designed and intended for use in military/aerospace applications or environments. Buyer acknowledges and agrees that any military or aerospace use of TI components which have *not* been so designated is solely at the Buyer's risk, and that Buyer is solely responsible for compliance with all legal and regulatory requirements in connection with such use.

TI has specifically designated certain components as meeting ISO/TS16949 requirements, mainly for automotive use. In any case of use of non-designated products, TI will not be responsible for any failure to meet ISO/TS16949.

Products Applications

Audio www.ti.com/audio Automotive and Transportation www.ti.com/automotive Communications and Telecom **Amplifiers** amplifier.ti.com www.ti.com/communications **Data Converters** dataconverter.ti.com Computers and Peripherals www.ti.com/computers **DLP® Products** www.dlp.com Consumer Electronics www.ti.com/consumer-apps

DSP **Energy and Lighting** dsp.ti.com www.ti.com/energy Clocks and Timers www.ti.com/clocks Industrial www.ti.com/industrial Interface interface.ti.com Medical www.ti.com/medical logic.ti.com Logic Security www.ti.com/security

Power Mgmt power.ti.com Space, Avionics and Defense www.ti.com/space-avionics-defense

Microcontrollers <u>microcontroller.ti.com</u> Video and Imaging <u>www.ti.com/video</u>

RFID www.ti-rfid.com

OMAP Applications Processors www.ti.com/omap TI E2E Community e2e.ti.com

Wireless Connectivity <u>www.ti.com/wirelessconnectivity</u>