

HMI Solution & Graphic Products



Hardware manual

		E INTELLIGENT DISPL	$A \lor 7$ 7 1 1 1 1 1 1 1 1 1 1
SPECIFICATION	IPRUURANINADL	E INTELLIGENT DISPL	AT / WVIJA

\sim 1	A 1		TE	\sim
ᇈᆫ	.AI	IKI	ITE	L

CHAPTER 1: VERSION'S HISTORICAL BACKGROUND	3
CHAPTER 2: GENERAL DESCRIPTION	4
CHAPTER 3: LIST OF ENVIRONMENTAL REQUIREMENTS	5
ENVIRONMENTAL NORMS AND EMC	5
CHAPTER 4: SPECIFICATION OF THE PROGRAMMABLE INTELLIGENT DISPLAY	6
MECHANICAL AND ENVIRONMENTAL CHARACTERISTICS	6
HMI CHARACTERISTICS	6
IO SPECIFICATION	6
ELECTRICAL CHARACTERISTICS	7
CHAPTER 5: PIN OUT	8
CHAPTER 6: DESCRIPTION OF CONNECTIONS	10
CONNECTOR USB	10
CONNECTOR V1 & V2	10
CONNECTOR FROM J1 TO J7	10
<u> Chapter 7: Embedded main Board – <i>Master Mode Version</i></u>	10
MECHANICAL CONSTRAINTS	11
ELECTRICAL CHARACTRISTICS	12
CHAPTER 8: MECHANICAL DESCRIPTION	13
CHAPTER 9: MOUNTING RECOMMENDATION	16
CHAPTER 10: CLAIRITEC'S CONTACT	19

CLAIRITEC

ERREUR! SIGNET NON DEFINI.

CLAIRITEC 13/03/2017	DOC-20170313-1B-UK	Page 2 / 20
Classification: CONFIDENTIAL	Copy or communication inhibited without written authori	zation from Clairitec

CHAPTER 1: VERSION'S HISTORICAL BACKGROUND

Reference	Modifications	Date
DOC-20160313-1A-UK	Creation	13/03/2017
DOC-20160313-1B-UK	Colors number and casings modification	10/10/2018

CLAIRITEC 13/03/2017	DOC-20170313-1B-UK	Page 3 / 20
Classification: CONFIDENTIAL	Copy or communication inhibited without written authori	ization from Clairitec

CHAPTER 2: GENERAL DESCRIPTION

The Programmable Intelligent Display is a "Plug & Play" graphic display module with integrated specific inputs and outputs. This product is developed & produced in France.

It consists of a TFT-LCD 7" WVGA (800 x 480 pixels) touchscreen display driven by an integrated HMI board from CLAIRITEC and an I/O management board. All these components are integrated into an IP65 protected casing. The Programmable Intelligent Display is EMC compliant and withstands a temperature range from -20°C to +70°C. It can easily fit into electronic equipment thanks to the modular structure of the casing.






Figure 1 – Casing types

The product range consists of different versions, allowing for various application types. It can be used in 2 different modes: slave and master mode:





CLAIRITEC 13/03/2017	DOC-20170313-1B-UK	Page 4 / 20
Classification: CONFIDENTIAL	Copy or communication inhibited without written authori	ization from Clairitec

CHAPTER 3: LIST OF ENVIRONMENTAL REQUIREMENTS

ENVIRONMENTAL NORMS AND EMC

The following table lists the environmental and EMC requirements that the Programmable Intelligent Display meets.

Norm	Minimum required				
	Environmental				
RoHS	All the components used in the Programmable Intelligent Display respect the RoHS norm				
	Electromagnetic compatibility (electronic board alone)				
NF EN-61000-4-3	Susceptibility 30 MHz - 1 GHz, 25Watt 10V/m				
NF EN-55022	Conducted emission 150Khz – 30 MHz class B				
	Radiated emission 30Mhz – 1Ghz class B				
NF-EN-61000-4-2	Protected against 8kV electrostatic discharge in the air, 4kV at contact				
UL 94 V-0	E76251 PCB agreement				
	Mechanical				
IP65	The front side is waterproof with the "from the front" casing				
IP40	All the components are protected by this norm				
Vesa 75x75	The "surface" and "table-top" casings are compatible with the VESA 75x75 system				

WARNING: Any handling on the electronic board involves the risk of electrostatic discharge (ESD), which could destroy components.

We strongly advise you to wear an antistatic wrist strap connected to Earth. Similarly, the electronic boards must be transported inside a specific antistatic packaging

CLAIRITEC 13/03/2017	DOC-20170313-1B-UK	Page 5 / 20
Classification:	Copy or communication inhibited without written author	ization from Clairitec

CHAPTER 4: SPECIFICATION OF THE PROGRAMMABLE INTELLIGENT DISPLAY

MECHANICAL AND ENVIRONMENTAL CHARACTERISTICS

<u>Item</u>	Specifications
Size	7" Diagonal
Resolution	800 x RGB x 480 dots (WVGA)
Viewing direction	6 o'clock
Viewing area	155.3 (W) x 94.3 (H) mm
Horizontal / Vertical flip	Available
Backlight	White LED
Brightness	400 cd/m ²
Viewing angle (typ.)	120° Vertical / 140° Horizontal
Touch screen	4-wire resistive / 1 million touch times by finger
	Capacitive / Minimum of 50 million touch times by finger
Operating temperature	-20°C ~ +70°C
Storage temperature	-30°C ~ +80°C
EMC compliant	NF-EN55022 class B (Frequency range 150 kHz to 2 GHz)
	NF-EN61000-4-2 (8 kV contact discharge / 15 kV air discharge)
	NF-EN61000-4-3 (Frequency range : 30 MHz to 1 GHz – 10 V/m)
IP Certification	IP65 on the front side with recessed "from the front" casing
	IP40 on the other sides.

HMI CHARACTERISTICS

Item	Specifications		
Color LCD Management	262k colors (display) – 16M (controller)		
	TFT transmissive active matrix		
Touchscreen Management	Advanced clicking area processing		
Graphic Engine	Advanced display algorithms		
Graphic layer Management	Two layers dynamically managed		
Storage Memory	32 Mb		
Graphical Layout Management	The GraphConverter®3 software tool enables you to build your HMI's graphic library and user interface and upload it to the HMI board's flash memory		

10 SPECIFICATION

	Digital	Analogic	Relay	Thermocouple	PT100	PWM	Internal RTC	Internal Buzzer
Input	6	5	-	2	1	-		,
Output	6	2	6	-	-	2	1	1

CLAIRITEC 13/03/2017	DOC-20170313-1B-UK	Page 6 / 20
Classification: CONFIDENTIAL	Copy or communication inhibited without written author	ization from Clairitec


ELECTRICAL CHARACTERISTICS


	Item	Symbol	Min	Тур	Max	Unit
	Power Supply voltage	Vcc	12	-	36	V
Power	Power Supply consumption*	Icc	260	-	TBC	mA
	Max Intensity	I _{sat}	-	-	2	Α
RS232	speed transmission	Bds	9,6	-	355	kBd
RS485	speed transmission	Bds	9,6	-	355	kBd
CAN	CAN 2.0B	Bds	100	-	500	kBd
Heb	voltage reference	V _{USB}	2.7	5	5.5	V
USB	Continuous output current	lusa	0	-	500	mA
	PWM voltage high level	V _{PWM} OH	-	Vcc	-	V
	PWM voltage low level	V _{PWM} LH	-	0	-	V
PWM	PWM intensity	V _{PWM} I	0	-	100	mΑ
	Frequency	V _{PWM} F	10	-	500k	Hz
	Duty cycle	V _{PWM Dt}	0	-	100	%
Thermocouple	Temperature range	T° MIN MAX	TBM	-	TBM	°C
PT100	Temperature range	T° MIN MAX	TBM	-	TBM	°C
Analag Innut	Voltage	V _{in MAX}	0	-	10	V
Analog Input	Resolution	R	-	10	-	bit
	Voltage	Vout MAX	0	-	10	V
Analas Outnut	Frequence	f	0	-	3	kHz
Analog Output	Intensity	lout	0	-	20	mΑ
	Resolution	R	-	8	-	bit
Dolov NO	Intensity	l _{in}	0	-	2	Α
Relay NO	Voltage	Vin	0	-	220	Vdc
Dolov NO/NC	Intensity	lin	0	-	2	Α
Relay NO/NC	Voltage	V _{in}	0	-	220	Vdc
	Voltage Com	COM	5.5	-	40	V
Digital Output	Voltage Out	Vout	0	-	COM	V
-	Intensity per channel	I _{max}	0	-	2	Α
Digital Input	Voltage Digital Input	Vin	0	-	Vcc	V


^{*}Without peripherals

CLAIRITEC 13/03/2017	DOC-20170313-1B-UK	Page 7 / 20
Classification: CONFIDENTIAL	Copy or communication inhibited without written authori	ization from Clairitec

CHAPTER 5: PIN OUT







CLAIRITEC 13/03/2017	DOC-20170313-1B-UK	Page 8 / 20
Classification:	Copy or communication inhibited without written author	ization from Clairitec

	1	Power Supply	DOWED
	2	GND	POWER
	3	CAN L	
_	4	CAN H	
7	5	RS485 A	
	6	RS485 B RS232 TX	COMMUNICATIONS
	7	RS485 Z RS232 RX	
	8	RS485 Y	
	1	Output PWM 2	DWM OUTDUTS
	2	Output PWM 1	PWM OUTPUTS
	3	Thermocouple 2 +	
75	4	Thermocouple 2 -	
٦	5	Thermocouple 1 +	THERMAL INPUTS
	6	Thermocouple 1 -	THERWAL INPUTS
	7	PT100	
	8	GND	
	1	Analog Input 5	
	2	Analog Input 4	
	3	Analog Input 3	ANALOG INPUTS
J3	4	Analog Input 2	
ا ت	5	Analog Input 1	
	6	GND	POWER
	7	Analog Ouput 1	ANALOG OUTPUTS
	8	Analog Ouput 2	711471200 0011 010
	1	GND	POWER
	2	Digital Input 6	
	3	Digital Input 5	
4	4	Digital Input 4	DIGITAL INPUTS
]	5	Digital Input 3	BIOTIAL IIII 010
	6	Digital Input 2	
	7	Digital Input 1	
	8	GND	POWER
	1	Power Supply	
	2	Digital Output COM	
	3	Digital Output 1	1
J5	4	Digital Output 2	
	5	Digital Output 3	DIOITAL OLITBUTO
	6	Digital Output 4	DIGITAL OUTPUTS
	7 8	Digital Output 5 Digital Output 6	
	1	Digital Output 7	
	2	Digital Output 8	
	3	Relays 2 NO	
	4	Relays 2	
96	5	Relays 2 NC	
	6	Relays 1 NO	RELAYS NO/NC
	7	Relays 1	
	8	Relays 1 NC	
	1	Relays 4 -	
	2	Relays 4 +	1
	3	Relays 3 -	1
2	4	Relays 3 +	DELAVE
ا ب ∣	5	Relays 2 -	RELAYS
	6	Relays 2 +	
	7	Relays 1 -	
1	8	Relays 1 +	


CLAIRITEC 13/03/2017	DOC-20170313-1B-UK	Page 9 / 20
Classification:	Copy or communication inhibited without written author	ization from Clairitec

CHAPTER 6: DESCRIPTION OF CONNECTIONS

The Clairitec Programmable Intelligent Display has three different connectors as shown in the drawing below:

CONNECTOR USB


This connector allows you to update the firmware and the graphic user interface via a computer or an USB key. Thanks to the transfer via USB connection, the loading time is decreased. It is required a standard adapter USB -> mini USB, available in the starter kit.



Pin	1/0	Description
1	Power	Power Supply +5V / 500mA max
2	1/0	USB -
3	1/0	USB +
4	-	Reserved
5	Power	GND


CONNECTOR V1 & V2

This connector allows you to directly connect to cameras with a 75Ω impedance male connector. It is recommended to be used with the MCX 75Ω impedance female connector, like the <u>R213182007</u> Radiall component reference or the <u>73415-4490</u> Molex component reference.



Connector	I/O	Description
1	Video 1	Signal PAL or NTSC
2	Video 2	Signal PAL or NTSC

CONNECTOR FROM J1 TO J7



There are many different crosslinks models for this Plug and play connector:


- Wurth 691361300008
- Wurth 691368300008B
- Wurth <u>691366310008</u>
- Wurth 691363310008

CHAPTER 7: EMBEDDED MAIN BOARD - MASTER MODE VERSION

CLAIRITEC 13/03/2017	DOC-20170313-1B-UK	Page 10 / 20
Classification:	Copy or communication inhibited without written author	ization from Clairitec


To be operated in Master mode, our system needs to embed a board which is programed like a state machine. Moreover, this board can integrate other specific I/O pinouts: protocol communication, and electronic system. Clairitec provides a standard main board, to which additional connectors or modules can be added upon request. You can also choose your own processor and schematic circuit.

The following figures present the maximal and minimal dimension of this board. You can find this board dimension on the STEP file attached.




As can be seen in this scheme, the programmable board is placed above the HMI board. It is fixed by a screw in the middle and gets connected to the HMI board through a number of connectors (left and right).

MECHANICAL CONSTRAINTS



The embedded main board cannot be smaller than the figure cannot be higher than 7mm on the upper side, and lower than 8,50mm on the bottom side. Beware of the connector and the screw hole.


CLAIRITEC 13/03/2017	DOC-20170313-1B-UK	Page 11 / 20
Classification: CONFIDENTIAL	Copy or communication inhibited without written author	ization from Clairitec



The embedded main board cannot be bigger than the figure above (these dimensions are the maximum size. Components cannot be higher than 7mm on the upper side, and lower than 8,50mm on the bottom side. An exception is the right-hand bottom side (marked with crosses): Here components can go down to 11 mm. Beware of the connector and the screw hole.

ELECTRICAL CHARACTRISTICS


The mechanical constraints show you that there is 2 connectors Male Barrel 1x10 with a 2,54mm step. This connectors allow to be connected with our main board.





	Item	Symbol	Min	Тур	Max	Unit
5V	Power Supply voltage	V _{cc}	-	5	-	V
	Power Supply consumption	Icc	0	-	500	mA
3V3	Power Supply voltage	Vcc	-	3.3	-	V
	Power Supply consumption	Icc	0	-	300	mA
RS232 TTL *	Bauderate	Bds	9,6	-	355	kBd
CAN 2.0B *	Bauderate	Bds	100	-	500	kBd
I2C	Address Used - TBC	Addr	58	3 59 55	38	Hex
	Frequency - TBC	f	-	391	-	kHz
Adding	Intensity per Output	lout	0	-	3	Α


^{*} PROGRAMMABLE INTELLIGENT DISPLAY COMMANDS ONLY


CLAIRITEC 13/03/2017	DOC-20170313-1B-UK	Page 12 / 20
Classification:	Copy or communication inhibited without written authori	ization from Clairitec














CHAPTER 10: CLAIRITEC'S CONTACT

Clairitec

CLAIRITEC 11 avenue Henri Becquerel 33700 Mérignac FRANCE

Website: www.clairitec.com

Clairitec's services

Customer relation service: contact@clairitec.com

Technical support service: support@clairitec.com











11, avenue Henri Bequerel - 33700 - MERIGNAC - FRANCE

Email: contact@clairitec.com www.clairitec.com