
High Power LED Series 3535 Ceramic LH351HRed 660nm



Features & Benefits

- Package : 2pad design package with Al2O3
- Dimension : 3.5 mm X 3.5 mm
- Technology : AlGaInP
- Operates at a maximum current of up to 1.0 A





Applications

• Horticulture



Table of Contents

1.	Characteristics	 3
2.	Product Code Information	 4
3.	Typical Characteristics Graphs	 6
4.	Outline Drawing & Dimension	 8
5.	Reliability Test Items & Conditions	 9
6.	Soldering Conditions	 10
7.	Tape & Reel	 11
8.	Label Structure	 13
9.	Packing Structure	 14
10.	Precautions in Handling & Use	 16

1. Characteristics

a) Absolute Maximum Rating

ltem	Symbol	Rating	Unit	Condition
Ambient / Operating Temperature	Ta	-40 ~ +105	٥C	Note 1)*
Storage Temperature	T _{stg}	-40 ~ +105	٥C	-
LED Junction Temperature	Tj	125	٥C	-
Forward Current (Tj: 25 °C)	l _F	1000	mA	Note 2)*-
Reverse Voltage ((@ 10 mA)	Vr	1.1	V	-
Assembly Process Temperature		280 <10	°C s	-
ESD (HBM)	-	±8	kV	-

Notes:

1) Refer to the derating curve, '3. Typical Characteristics Graph', for proper driving current that maintained below maximum junction temperature.

2) Unpredictable performance may be resulted by driving the product at above Max. IF. But there will be no damage to the product.

b) Electro-optical Characteristics

ltem	Unit	Cond	ition	Value	
item	Onic	I _F (mA)	T _j (°C)	Тур.	
Radiant Power (Φ_{E})	mW	350	25	425	
Forward Voltage (V_F)	V	350	25	2.2	
Thermal Resistance (junction to solder point)	°C/W	350	25	2.5	
Beam Angle	0	350	25	120	
Peak wavelength (λ_P)	nm	350	25	660	
Dominant wavelength (λ_D)	nm	350	25	643	
Photosynthetic Photon Flux	µmol/s	350	25	2.4	

Notes:

1) Samsung maintains measurement tolerance of: Radiant Power = ± 7 %, forward voltage = ± 0.1 V, Wavelength = ± 2 nm

2) Characteristics @ 25 °C are for reference only

2. Product Code Information

1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18
S																	

Digit	Digit PKG Information		Specification
1 2 3	Samsung Package High Power	SPH	
4 5	Color	RD	Red
6	Product Version	2	
78	Product	L3	LH351 Series
9	Lens Type	D	Dome lens
10	Internal Code	н	
11	Not Defined	0	Default
12	CRI & Sorting Temperature	0	Default 25 °C
13 14	Forward Voltage (V)	D 5	1.9 ~ 2.4
15 16	Wavelength (nm)	W 4	650 ~ 670
17 18	Radiant Power (mW)	МО	390 ~

a) Voltage Bins ($I_F = 350 \text{ mA}, T_j = 25 \text{ }^{\circ}\text{C}$)

Product Code	Voltage Rank	Voltage Bin	Voltage Range (V)
SPHRD2L3DH00D5W4M0	D5	D5	1.9 ~ 2.4


b) Wavelength Bins (I_F = 350 mA, T_j = 25 °C)

Product Code	Wavelength Rank	Wavelength Bin	Wavelength Range (nm)
SPHRD2L3DH00D5W4M0	W4	W4	650 ~ 670

c) Radiant Power Bins ($I_F = 350 \text{ mA}, T_j = 25 \text{ °C}$)


Product Code	Power Rank	Power Bin	Power Range (mW)
SPHRD2L3DH00D5W4M0	MO	M0	390 ~


3. Typical Characteristics Graphs



a) Spectrum Distribution ($I_F = 350 \text{ mA}, T_j = 25 \text{ °C}$)


b) Forward Current Characteristics (T_j = 25 °C)







3. Typical Characteristics Graphs

c) Temperature Characteristics $(I_F = 350 \text{ mA})$




e) Derating Curve and Beam Angle Characteristics $(I_F = 350 \text{ mA})$





4. Outline Drawing & Dimension



Notes:

- 1) This LED has built-in ESD protection device(s) connected in parallel to LED chip(s).
- 2) The thermal pad is electrically isolated from the anode and cathode contact pads.
- 3) T_s point and measurement method:
 - (1) Measure the nearest point to thermal pad as shown above. If necessary, remove PSR of PCB to reach T_s point.
 - 2 All pads must be soldered to the PCB to dissipate heat properly, otherwise the LED can be damaged.

Precautions:

- Pressure on the LEDs will influence to the reliability of the LEDs. Precautions should be taken to avoid strong pressure on the LEDs. Do not put stress on the LEDs during heating.
- 2) Re-soldering should not be done after the LEDs have been soldered. If re-soldering is unavoidable, LED's characteristics should be carefully checked before and after such repair.
- Do not stack assembled PCBs together. Since materials of LEDs is soft, abrasion between two PCB assembled with LED might cause catastrophic failure of the LEDs.

5. Reliability Test Items & Conditions

a) Test Items

Test Item	Test Condition	Test Hour / Cycle	Sample Size
High Temperature Life Test	85 ºC, DC Derating I _F	1000 h	22
High Temperature Humidity Life Test	85 ⁰C, 85 % RH, DC Derating I⊧	1000 h	22
Low Temperature Life Test	-40 ºC, DC Derating I⊧	1000 h	22
Powered Temperature Cycle	-40 °C / 85 °C each 20 min, 100 min transfer power on/off each 5 min, DC Derating I⊧	100 cycles	11
Temperature Cycling	-45 °C / 15 min \leftrightarrow 125 °C / 15 min temperature change within 5 min	500 cycles	100
High Temperature Storage	120 °C	1000 h	11
Low Temperature Storage	-40 °C	1000 h	11
ESD (HBM)	R ₁ : 10 MΩ R ₂ : 1.5 kΩ C: 100 pF V: ±8 kV	5 times	30
ESD (MM)	R1: 10 MΩ R2: 0 C: 200 pF V: ±0.5 kV	5 times	30
Vibration Test	20~2000~20 Hz, 200 m/s ² , sweep 4 min X, Y, Z 3 direction, each 1 cycle	4 cycles	11
Mechanical Shock Test	1500 g, 0.5 ms 3 shocks each X-Y-Z axis	5 cycles	11


b) Criteria for Judging the Damage

ltem	Symbol	Test Condition	Limit		
item	Symbol	(T _j = 25 ^o C)	Min.	Max.	
Forward Voltage	VF	$I_F = 350 \text{ mA}$	Init. Value * 0.9	Init. Value * 1.1	
Luminous Flux	Φv	I _F = 350 mA	Init. Value * 0.7	Init. Value * 1.1	

6. Soldering Conditions

a) Reflow Conditions (Pb free)

Reflow frequency: 2 times max.




b) Manual Soldering Conditions


Not more than 5 seconds @ max. 300 °C, under soldering iron.

7. Tape & Reel


a) Taping Dimension

(unit: mm)





(unit: mm)




Notes:

- 1) Quantity: The quantity/reel is 1,000 pcs
- 2) Cumulative tolerance: Cumulative tolerance / 10 pitches is ±0.2 mm
- Adhesion strength of cover tape: Adhesion strength is 0.1-0.7 N when the cover tape is turned off from the carrier tape at 10° angle to the carrier tape
- 4) Packaging: P/N, Manufacturing data code no. and quantity are indicated on the aluminum packing bag

8. Label Structure

a) Label Structure




Note: Denoted bin code and product code above is only an example (see description on page 4)

Bin Code:

- (a) (b): Forward Voltage bin (refer to page 5)
- ©d: Wavelength bin (refer to page 5)
- (e) f): Radiant Power bin (refer to page 5)

b) Lot Number

The lot number is composed of the following characters:




123456789/Iabc / 1,000 pcs

1), 2	:	Production site (GB : Nanchang, China)
3	:	Product state (A: Normal, B: Bulk, C: First Production, R: Reproduction, S: Sample)
4	:	Year (C: 2018, D: 2019, E: 2020,)
(5)	:	Month (1~9, A, B, C)
6	:	Day (1~9, A, B~V)
789	:	Product serial number (001 ~ 999)
abc	:	Reel number (001 ~ 999)

9. Packing Structure

a) Packing Process



Outer Box


Material: Paper SW(B)

Turne		Note		
Туре	(a)	(b)	(c)	Note
7 inch (L)	245 ± 5	220 ± 5	182 ± 5	Up to 8 reels
7 inch (S)	245 ± 5	220 ± 5	86 ± 5	Up to 4 reels





Ω





c) Silica Gel & Humidity Indicator Card inside Aluminum Vinyl Bag



10. Precautions in Handling & Use

- For over-current protection, users are recommended to apply resistors connected in series with the LEDs to mitigate sudden change of the forward current caused by shift of forward voltage.
- 2) This device should not be used in any type of fluid such as water, oil, organic solvent, etc. When cleaning is required, IPA is recommended as the cleaning agent. Some solvent-based cleaning agent may damage the silicone resins used in the device.
- 3) When the device is in operation, the forward current should be carefully determined considering the maximum ambient temperature and corresponding junction temperature.
- 4) LEDs must be stored in a clean environment. If the LEDs are to be stored for three months or more after being shipped from Samsung, they should be packed with a nitrogen-filled container (shelf life of sealed bags is 12 months at temperature 0~40 °C, 0~90 % RH).
- After storage bag is opened, device subjected to soldering, solder reflow, or other high temperature processes must be:
 a. Mounted within 672 hours (28 days) at an assembly line with a condition of no more than 30 °C / 60 % RH, or
 b. Stored at <10 % RH
- 6) Repack unused devices with anti-moisture packing, fold to close any opening and then store in a dry place.
- 7) Devices require baking before mounting, if humidity card reading is >60 % at 23 ± 5 °C.
- 8) Devices must be baked for 1 hour at 60 ± 5 °C, if baking is required.
- 9) The LEDs are sensitive to the static electricity and surge current. It is recommended to use a wrist band or antielectrostatic glove when handling the LEDs. If voltage exceeding the absolute maximum rating is applied to LEDs, it may cause damage or even destruction to LED devices. Damaged LEDs may show some unusual characteristics such as increase in leakage current, lowered turn-on voltage, or abnormal lighting of LEDs at low current.
- 10) VOCs (Volatile Organic Compounds) can be generated from adhesives, flux, hardener or organic additives used in luminaires (fixtures). Transparent LED silicone encapsulant is permeable to those chemicals and they may lead to a discoloration of encapsulant when they exposed to heat or light. This phenomenon can cause a significant loss of light emitted (output) from the luminaires. In order to prevent these problems, we recommend users to know the physical properties of materials used in luminaires and they must be carefully selected.

About Samsung Electronics Co., Ltd.

Samsung Electronics Co., Ltd. inspires the world and shapes the future with transformative ideas and technologies, redefining the worlds of TVs, smartphones, wearable devices, tablets, cameras, digital appliances, printers, medical equipment, network systems and semiconductors.

We are also leading in the Internet of Things space through, among others, our Digital Health and Smart Home initiatives. We employ 307,000 people across 84 countries. To discover more, please visit our official website at www.samsung.com and our official blog at global.samsungtomorrow.com.

Copyright © 2016 Samsung Electronics Co., Ltd. All rights reserved. Samsung is a registered trademark of Samsung Electronics Co., Ltd. Specifications and designs are subject to change without notice. Non-metric weights and measurements are approximate. All data were deemed correct at time of creation. Samsung is not liable for errors or omissions. All brand, product, service names and logos are trademarks and/or registered trademarks

of their respective owners and are hereby recognized and acknowledged.

Samsung Electronics Co., Ltd. 1, Samsung ro Giheung-gu Yongin-si, Gyeonggi-do, 17113 KOREA

www.samsungled.com

