

Crystal Units List

Sh		For	Number	-						Frequer	icy R	ange	(MH	z)						
ape	Model	Automotive	of terminals	Page	3	4	5			10	20	3) 40)	50	70		10	0	200
	Tuning Fork Crystal L	Jnit (kHz	range)					- I		1										
	NX1610SA		2	3																
	NX2012SA		2	5																
	NX3215SA		2	7																
	NX1610SE (Low ESR)		2	4																
	NX2012SE (Low ESR)		2	6																
	NX3215SE (Low ESR)		2	8	• 32.768	3kHz	<u>z</u>													
	NX2012SA	0	2	5																
	NX3215SA	0	2	6																
S L	NX3215SD (Enhanced products of solder cracking resistance)	0	2	9																
ırfa	NX3215SF (For Specially controlled medical devices Class III)		2	10																
c	Crystal Unit with built	-in tempe	rature ser	isor (MHz	z range)			 												
e I	NX1210AC		4	11																
n o	NX1612SD		4	12																
u n	NX2016SF		4	13							Ļ									
t t	NX2016SF	0	4	15							Ļ									
ур	NX2520SG		4	14							Ļ									
e	Crystal Units (MHz rate)	inge) / Siz	ze : 1.0×0.	8mm						1	, î						_			
	NX1008AA		4	16																
	Crystal Units (MHz rate)	ange) / Siz	ze : 1.2×1	.0mm				 												
	NX1210AB		4	17																
	Crystal Units (MHz radius)	ange) / Siz	ze : 1.6×1	.2mm				 									_			
	NX1612SA		4	18											-					
	NX1612SA	0	4	19																
	Crystal Units (MHz radius)	ange) / Siz	ze : 2.0×1.	6mm				 												
	NX2016GC	0	2	21																
	NX2016SA		4	20											+					
	NX2016SA	0	4	22											+					
Shape	Model	For Automotive	Number of terminals	Page	3	4	5	'		10 Frequer	20 ncy Ra	3 ange	0 4 (MH:) z)	50	70	1	10	0	200
							*	Fu	und	amental		3	rd ov	erto	one				5th over	tone

For details, please see our website (https://www.ndk.com/).



Crystal Units List

Sh		For	Number	_				-			Fred	quency	Rang	e (N	/Hz)						
ape	Model	Automotive	of terminals	Page	3	4	5				10 L	2	20	30	40	5	0	70	1	100		200
	Crystal Units (MHz rate)	inge) / Siz	ze : 2.5×2	.0mm				<u>г г</u>	-	1 1			1		- 1		1			-		
	NX2520SA		4	23									1				1					
	Crystal Units (MHz radius)	inge) / Siz	ze : 3.2×2	.5mm					Ĵ		<u> </u>		1									
	NX3225GA		4	25																		
	NX3225GA	0	4	26]					
	NX3225GB	0	2	27																		
r f a	NX3225GD	0	2	28																		
с е	NX3225SA		4	24									1									
Э	NX3225SA	0	4	27																		
o L	NX3225SC	0	4	30									1									
⊐	Crystal Units (MHz radius)	inge) / Siz	ze:5.0×3	.2mm																		
-	NX5032GA		2	31																		
t y p	NX5032GA	0	2	32																		
0	NX5032SD	0	4	33									1									
	Crystal Units (MHz rate)	inge) / Siz	ze:8.0×4	.5mm					T						- 1		1					
	NX8045GB		2	34		ļ																
	NX8045GB	0	2	36																		
	NX8045GE	0	2	35		ļ																
	AT-41		2	37	[4							
Lead	AT-41CD2		2	37	[
mou	NR–2C		2	38																		
nting	NR–2B		2	38																		
type	RC-8		5	39]									
	NC-18C		2	39																		
Shap	Model	For	Number of	Page	3	4	5			IT	10	2	20	30	40	5	50	70	ΙŢ	100		200
ŏ			terminals								Free	quency	Rang	e (N	/Hz)						
							*		Fι	und	amen	tal		3rd	ove	erto	ne			5	5th ove	ertone

For details, please see our website (https://www.ndk.com/).



NX1610SA

For OA / AV / Mobile Communications

Features

- Ultra compact, thin, and light weight tuning fork crystal unit.
- •Ultra compact and thin. (1.6×1.0×0.45mm)
- •Excellent electric performance optimum for mobile communications, OA (office automation) and AV (audiovisual) applications are exhibited.
- •A surface-mount crystal oscillator. (Reflow soldering is possible.)
- •RoHS compliant. These can meet the requirements of re-flow profiling using leadfree solder.



Specifications

Item		NX16	510SA			
Standard		Standard		Optional		
Nominal Frequency (kHz)		32.768		32.768		
Operating Temperature Range (°C)		-40 to +85		-40 to +85 *1		
Storage Temperature Range (°C)		-40 to +85		-40 to +85 *1		
Level of Drive (µW)		0.1 (Max. 0.5)				
Frequency Tolerance (25 ±3 °C)		±20 × 10⁻6				
Turning Point (°C)		+25 ± 5		+25 ± 5		
Temperature Coefficient (/°C2)		Max. −0.04 × 10 ⁻⁶				
Load Capacitance (pF)	6.0	9.0	12.5	6.0 to 12.5		
Equivalent Series Resistance ($k\Omega$)		Max. 90		Max. 90 *1		
Shunt Capacitance (pF)		Тур. 1.3 / Мах. 1.6				
Insulation Resistance (MΩ)		Min. 500				
Specifications Number	STD-MUD-2	STD-MUD-2 STD-MUD-3 STD-MUD-1				

Please specify the model name, frequency, and specification number when you order products.

For futher questions regarding specifications, please feel free to contact us.

*1 If you have any other requests, NDK will study it.

*2 Ordering information: Overtone Order Fundamental, the Operating Temperature Range, Frequency Tolerance, and Load Capacitance. Ex. Model, Frequency (32.768000kHz 6digits),

S1:Fundamental - Operating Range(-40 to +85°C) - Frequency Tolerance(±20×10-6) - Load Capacitance (9pF)

- NX1610SA
- 32.768000kHz
- S1-4085-20-9





NX1610SE

For OA / AV / Mobile Communications

Features

- Tuning fork crystal unit with low ESR(Equivalent Series Resistance).
- •Low ESR achieves low power consumption.
- •Excellent electric performance optimum for mobile communications, OA (office automation) and AV (audiovisual) applications are exhibited.
- •A surface-mount crystal oscillator. (Reflow soldering is possible.)
- •Lead-free. Meets the requirements for re-flow profiling using lead-free solder.



Specifications

Item Model		NX16	10SE	
Standard		Standard		Optional
Nominal Frequency (kHz)		32.768		32.768
Operating Temperature Range (°C)		-40 to +85		-40 to +85 *1
Storage Temperature Range (°C)		-40 to +85		-40 to +85 *1
Level of Drive (µW)		0.1 (Max. 0.5)		0.1 (Max. 0.5) *1
Frequency Tolerance (25 ±3 °C)		±20 × 10 ⁻⁶		
Turning Point (°C)		+25 ± 5		+25 ± 5
Temperature Coefficient (/°C ²)		Max. –0.04 × 10 ⁻⁶		Max. –0.04 × 10 ⁻⁶
Load Capacitance (pF)	6.0	9.0	12.5	6.0 to 12.5
Equivalent Series Resistance (kΩ)		Max. 60 *1		
Shunt Capacitance (pF)		Тур. 1.55 / Мах. 1.85		
Insulation Resistance (MΩ)		Min. 500		
Specifications Number	STD-MUD-6	Refer to *2		

Please specify the model name, frequency, and specification number when you order products.

For futher questions regarding specifications, please feel free to contact us.

*1 If you have any other requests, NDK will study it.

*2 Ordering information: Overtone Order Fundamental, the Operating Temperature Range, Frequency Tolerance, and Load Capacitance. Ex. Model, Frequency (32.768000kHz 6digits),

S1:Fundamental - Operating Range(-40 to +85°C) - Frequency Tolerance(±20×10⁻⁶) - Load Capacitance (9pF) NX1610SE

32.768000kHz

S1-4085-20-9



Features

- Compact, thin, and light weight tuning fork crystal unit.
- •Compact and thin. (2.0×1.2×0.55mm)
- •Excellent electric performance optimum for mobile communications, OA (office automation) and AV (audiovisual) applications are exhibited.
- •A surface-mount crystal oscillator. (Reflow soldering is possible.) •RoHS compliant. These can meet the requirements of re-flow profiling
- using leadfree solder.
- •Conforms to AEC-Q200. (For Automotives)

Specifications

Item		NX2012SA								
Standard		Standard								
Main Application	For OA / AV	For OA / AV / Mobile Communication For Automotive					For OA / AV / Mobile Communication/ Automotive			
Nominal Frequency (kHz)			32.	768			32.768			
Operating Temperature Range (°C)		-40 to +85			-40 to +125		-40 to +85 *1			
Storage Temperature Range (°C)		-40 to +85 -40 to +125								
Level of Drive (µW)			0.1 (M	ax. 0.5)			0.1 (Max. 0.5) *1			
Frequency Tolerance (25 ±3 °C)			±20 :	× 10⁻ ⁶			±20 × 10 ⁻⁶			
Turning Point (°C)			+25	5±5			+25 ± 5			
Temperature Coefficient (/°C ²)			Max0.	04 × 10⁻ ⁶			Max. −0.04 × 10 ⁻⁶			
Load Capacitance (pF)	6.0	9.0	12.5	6.0	9.0	12.5	6.0 to 12.5 *1			
Equivalent Series Resistance ($k\Omega$)	Max. 80 Max. 120					Max. 80 *1				
Shunt Capacitance (pF)	Typ. 1.3/ Max. 1.6					Typ. 1.3/ Max. 1.6				
Insulation Resistance (MΩ)	Min. 500					Min. 500				
Specifications Number	STD-MUB-3	STD-MUB-2	STD-MUB-1	STD-MUT-3	STD-MUT-2	STD-MUT-1	Refer to *2			

Please specify the model name, frequency, and specification number when you order products.

For futher questions regarding specifications, please feel free to contact us.

*1 If you have any other requests, NDK will study it.

*2 Ordering information: Overtone Order Fundamental, the Operating Temperature Range, Frequency Tolerance, and Load Capacitance. Ex. Model, Frequency (32.768000kHz 6digits),

S1:Fundamental - Operating Range(-40 to +85°C) - Frequency Tolerance(±20×10-6) - Load Capacitance (9pF) NX2012SA

32.768000kHz S1-4085-20-9

Dimensions





For OA / AV / Mobile Communication / Automotives

Pb

RoHS Compliant

tive 2011/ ve (EU) 20



NX2012SA



NX2012SE

For OA / AV / Mobile Communications

Features

- Tuning fork crystal unit with low ESR(Equivalent Series Resistance).
- •Supports Microcontroller requiring low ESR. (ESR:Max. 50kΩ)
- •Excellent electric performance optimum for mobile communications, OA (office automation) and AV (audiovisual) applications are exhibited.
- •A surface-mount crystal oscillator. (Reflow soldering is possible.)
- •Lead-free. Meets the requirements for re-flow profiling using lead-free solder.



Pb Free RoHS Compliant Directive 2011/65/EU Directive (EU) 2015/863

Specifications

Item		NX2012SE					
Standard		Standard		Optional			
Nominal Frequency (kHz)		32.768		32.768			
Operating Temperature Range (°C)		-40 to +85		-40 to +85 *1			
Storage Temperature Range (°C)		-40 to +85		-40 to +85 *1			
Level of Drive (µW)	0.1 (Max. 0.5) 0.1 (Ma						
Frequency Tolerance (25 ±3 °C)		±20 × 10-6					
Turning Point (°C)		+25 ± 5		+25 ± 5			
Temperature Coefficient (/°C2)		Max0.04 × 10-6		Max. –0.04 × 10 ⁻⁶			
Load Capacitance (pF)	6.0	9.0	12.5	6.0 to 12.5			
Equivalent Series Resistance ($k\Omega$)		Max. 50 *1					
Shunt Capacitance (pF)		Тур. 1.7 / Мах. 2.0					
Insulation Resistance (MΩ)		Min. 500 Min.					
Specifications Number	STD-MUB-8	Refer to *2					

Please specify the model name, frequency, and specification number when you order products.

For futher questions regarding specifications, please feel free to contact us.

*1 If you have any other requests, NDK will study it.

*2 Ordering information: Overtone Order Fundamental, the Operating Temperature Range, Frequency Tolerance, and Load Capacitance. Ex. Model, Frequency (32.768000kHz 6digits),

S1:Fundamental - Operating Range(-40 to +85°C) - Frequency Tolerance(±20×10⁻⁶) - Load Capacitance (9pF)

NX2012SE

32.768000kHz

S1-4085-20-9





NX3215SA

For OA / AV / Mobile Communication / Automotives

Pb Free

RoHS Compliant

Directive 2011/65/EU Directive (EU) 2015/86

Features

Compact, thin, and light weight tuning fork crystal unit.

•Excellent electric performance optimum for mobile communications,

- OA (office automation) and AV (audiovisual) applications are exhibited. (For OA / AV / Mobile Communication)
- •Excellent heat resistance and environmental characteristics. (For Automotives)
- •Meet the requirements for re-flow profiling using lead-free solder.
- •Conforms to AEC-Q200. (For Automotives)

A9921 50

Specifications

Item		NX3215SA								
Standard		Standard								
Main Application	For OA / AV	For OA / AV / Mobile Communication For Automotive					For OA / AV / Mobile Communication/ Automotive			
Nominal Frequency (kHz)			32.	768			32.768			
Operating Temperature Range (°C)		-40 to +85			-40 to +125		-40 to +85 *1			
Storage Temperature Range (°C)	mperature Range (°C) -40 to +85			-40 to +85 -40 to +125						
Level of Drive (µW)			0.1 (M	ax. 0.5)			0.1 (Max. 0.5) *1			
Frequency Tolerance (25 ±3 °C)			±20 >	× 10⁻ ⁶			±20 × 10⁻6			
Turning Point (°C)			+25	5±5			+25 ± 5			
Temperature Coefficient (/°C ²)			Max. −0.	04 × 10⁻⁵			Max. −0.04 × 10 ⁻⁶			
Load Capacitance (pF)	6.0	9.0	12.5	6.0	9.0	12.5	6.0 to 12.5 *1			
Equivalent Series Resistance ($k\Omega$)	Max. 70 Max. 80					Max. 70 *1				
Shunt Capacitance (pF)	Typ. 1.0 / Max.1.5						Тур. 1.0 / Мах.1.5			
Insulation Resistance (MΩ)	Min. 500						Min. 500			
Specifications Number	STD-MUA-14	STD-MUA-14 STD-MUA-9 STD-MUA-8 STD-MUS-4 STD-MUS-3 STD-MUS-2					Refer to *2			

Please specify the model name, frequency, and specification number when you order products.

For futher questions regarding specifications, please feel free to contact us.

*1 If you have any other requests, NDK will study it.

*2 Ordering information: Overtone Order Fundamental, the Operating Temperature Range, Frequency Tolerance, and Load Capacitance. Ex. Model, Frequency (32.768000kHz 6digits),

S1:Fundamental - Operating Range(-40 to +85°C) - Frequency Tolerance(±20×10⁻⁶) - Load Capacitance (9pF)

- NX3215SA
- 32.768000kHz
- S1-4085-20-9





NX3215SE

For OA / AV / Mobile Communications

Features

- Tuning fork crystal unit with low ESR(Equivalent Series Resistance).
- •Supports Microcontroller requiring low ESR. (ESR:Max. 40kΩ)
- •Excellent electric performance optimum for mobile communications, OA (office automation) and AV (audiovisual) applications are exhibited.
- •A surface-mount crystal oscillator. (Reflow soldering is possible.)
- •Lead-free. Meets the requirements for re-flow profiling using lead-free solder.



Pb Free RoHS Compliant Directive 2011/65/EU

Specifications

Item Model		NX32	15SE	
Standard		Standard		Optional
Nominal Frequency		32.768kHz		32.768kHz
Operating Temperature Range (°C)		-40 to +85		-40 to +85 *1
Storage Temperature Range (°C)		-40 to +85		-40 to +85 *1
Level of Drive (µW)		0.1 (Max. 0.5)		0.1 (Max. 0.5) *1
Frequency Tolerance (25 ±3 °C)		±20 × 10 ⁻⁶ *1		
Turning Point (°C)		+25 ± 5		+25 ± 5
Temperature Coefficient (/°C2)		Max. –0.04 × 10 ⁻⁶		Max. –0.04 × 10⁻⁰
Load Capacitance (pF)	6.0	9.0	12.5	6.0 to 12.5 *1
Equivalent Series Resistance (kΩ)		Max. 40 *1		
Shunt Capacitance (pF)		Typ. 1.3 / Max. 1.6		
Insulation Resistance (MΩ)		Min. 500		
Specifications Number	STD-MUA-19	Refer to *2		

Please specify the model name, frequency, and specification number when you order products.

For futher questions regarding specifications, please feel free to contact us.

*1 If you have any other requests, NDK will study it.

*2 Ordering information: Overtone Order Fundamental, the Operating Temperature Range, Frequency Tolerance, and Load Capacitance. Ex. Model, Frequency (32.768000kHz 6digits),

S1:Fundamental - Operating Temperature Range (-40 to +85°C) - Frequency Tolerance (±20×10⁻⁶) - Load Capacitance (9pF) NX3215SE

32.768000kHz

S1-4085-20-9



6.0

STD-MUS-7

Please specify the model name, frequency, and specification number when you order products.

Level of Drive (µW) Frequency Tolerance (25 ±3 °C) Turning Point (°C) Temperature Coefficient (/°C2)

For futher questions regarding specifications, please feel free to contact us.

Model

*1 If you have any other requests, NDK will study it. *2 Ordering information: Overtone Order Fundamental, the Operating Temperature Range, Frequency Tolerance, and Load Capacitance. Ex. Model, Frequency (32.768000kHz 6digits),

S1:Fundamental - Operating Temperature Range (-40 to +85°C) - Frequency Tolerance(±20×10⁻⁶) - Load Capacitance (9pF) NX3215SD

32.768000kHz

S1-4085-20-9

Dimensions



NX3215SD

Features

Small surface-mount type tuning fork crystal unit for automotive. High resistance to solder cracking.

- Excellent heat resistance and environmental characteristics.
- •A surface-mount crystal oscillator. (Reflow soldering is possible.)
- •Meet the requirements for re-flow profiling using lead-free solder.
- •Conforms to AEC-Q200.

Specifications

Nominal Frequency (kHz)

Load Capacitance (pF)

Shunt Capacitance (pF)

Specifications Number

Insulation Resistance (M Ω)

Operating Temperature Range (°C)

Storage Temperature Range (°C)

Equivalent Series Resistance (kΩ)

Item

Standard



NX3215SD

12.5

STD-MUS-5

Standard

32.768

-40 to +125

-40 to +125

0.1 (Max. 0.5)

±20 × 10⁻⁶

+25 ± 5

Max. -0.04 × 10⁻⁶

9.0

Max. 80

Typ. 1.2 / Max.1.5

Min. 500

STD-MUS-6



Optional

32.768

-40 to +125 *1

-40 to +125 *1

0.1 (Max. 0.5) *1

±20 × 10⁻⁶ *1

+25 ± 5

Max. -0.04 × 10⁻⁶

6.0 to 12.5 *1

Max. 80 *1

Typ. 1.2 / Max.1.5

Min. 500

Refer to *2

MAD67MI



NX3215SF

For Specially controlled medical devices Class III

Features

Compact, thin, and light weight tuning fork crystal unit.

- High quality has been achieved through process design compatible with specially controlled medical devices class III.
- •Excellent heat resistance and environmental characteristics ensure high reliability.
- •Meet the requirements for re-flow profiling using lead-free solder.





Pb Free

Specifications

Item		NX32	15SF			
Standard		Standard		Optional		
Nominal Frequency (kHz)		32.768		32.768		
Operating Temperature Range (°C)		-40 to +125		-40 to +125 *1		
Storage Temperature Range (°C)		-40 to +125		-40 to +125 *1		
Level of Drive (µW)		0.1 (Max. 0.5)		0.1 (Max. 0.5) *1		
Frequency Tolerance (25 ±3 °C)		±20 × 10 ⁻⁶				
Turning Point (°C)		+25 ± 5		+25 ± 5		
Temperature Coefficient (/°C2)		Max0.04 × 10 ⁻⁶				
Load Capacitance	6.0	9.0	12.5	6.0 to 12.5		
Equivalent Series Resistance (kΩ)			Max. 70 *1			
Shunt Capacitance (pF)		Typ. 1.0 / Max.1.5				
Insulation Resistance (MΩ)		Min. 500				
Specifications Number	STD-MUP-1	Refer to *2				

Please specify the model name, frequency, and specification number when you order products.

For futher questions regarding specifications, please feel free to contact us.

*1 If you have any other requests, NDK will study it.

*2 Ordering information: Overtone Order Fundamental, the Operating Temperature Range, Frequency Tolerance, and Load Capacitance. Ex. Model, Frequency (32.768000kHz 6digits),

S1:Fundamental - Operating Range(-40 to +85°C) - Frequency Tolerance(±20×10⁻⁶) - Load Capacitance (9pF) NX3215SF

32.768000kHz

S1-4085-20-9





NX1210AC

For Mobile Communications

Features

Crystal Unit with built-in Thermistor construction.

- Minimize circuit design space by combining crystal unit into one component.
- (Presently, Crystal unit and temperature sensor is mounted in one board separately.)Placing temperature sensor(Thermistor) close to Crystal blank in one airtight housing
- Placing temperature sensor (mermistor) close to crystal blank in one antight nousi can detect more precise crystal blank temperature. Improvement on frequency temperature compensation compared to present Crystal unit.
- Single cavity housing which is ideal to module applications.
- External configuration size is 1.2x1.0mm typ., H0.55 mm Max.
- A surface-mount crystal oscillator. (Reflow soldering is possible.)
- Lead-free. Meets the requirements for re-flow profiling using lead-free solder.



Specifications

Item Model	NX1	210AC
Standard	Standard	Optional
Nominal Frequency (MHz)	38.4 ≤ F ≤ 96	38.4 ≤ F ≤ 96
Overtone Order	Fundamental	Fundamental
Frequency Tolerance (25 ± 3°C)	±12 × 10 ⁻⁶	±12 × 10 ⁻⁶
Frequency versus Temperature Characteristics (with reference to +24.5 °C)	$\pm 12 \times 10^{-6}$	Please contact us about temp extended case, *1
Operating Temperature Range (°C)	-30 to +85	Please contact us about temp extended case, *1
Storage Temperature Range (°C)	-40 to +85	-40 to +85
Equivalent Series Resistance	Refer to *2	Refer to *2
Level of Drive (µW)	10 (Max. 100)	10 (Max. 100)
Load Capacitance (pF)	7	6 to 12
Frequency Aging (+25°C)		Max. ±3 × 10 ⁻⁶ / year *1
Specifications Number	STD-CTR-1	Refer to *3

Please specify the model name, frequency, and specification number when you order products.

For futher questions regarding specifications, please feel free to contact us.

*1 If you have any other requests, NDK will study it.

*3 Ordering information: Overtone Order Fundamental / 3rd Overtone, the Operating Temperature Range, Frequency versus Temperature Characteristics, Frequency Tolerance, and Load Capacitance.

Ex. Model, Frequency (38.400000MHz 6digits), S1:Fundamental or S3:3rd Overtone

- Operating Temperature Range (-30 to +85°C) - Frequency versus Temperature Characteristics (±12×10⁻⁶)

- Frequency Tolerance (±12×10-6) - Load Capacitance (7pF)

NX1210AC

S1-3085-12-12-7

Dimensions



*2 Equivalent Series Resistance

Nominal Frequency (MHz)	Equivalent Series Resistance Max. (Ω)
38.4 ≤ F < 52	60
52 ≤ F < 76.8	50
76.8 ≤ F ≤ 96	40

Resistance (R25)	100k Ω ± 1 %
B-Constant (B25-50)	4250K ± 1 %

^{38.400000}MHz



NX1612SD

For Mobile Communications

Features

Crystal Unit with built-in Thermistor construction.

- Minimize circuit design space by combining crystal unit into one component.
- $(\ensuremath{\mathsf{Presently}}, \ensuremath{\mathsf{Crystal}}\xspace{\ensuremath{\mathsf{unit}}}\xspace{\ensuremath{\mathsf{and}}}\xspace{\ensuremath{\mathsf{temperature}}\xspace{\ensuremath{\mathsf{sensuremath{\mathsf{mom}}}\xspace{\ensuremath{\mathsf{norm}}\xspace{\ensuremath{\mathsf{ch}}\xspace{\ensuremath{\mathsf{sensuremath{\mathsf{mom}}}\xspace{\ensuremath{\mathsf{norm}}\xspace{\ensuremath{norm}}\xspace{\ensuremath{norm}}\xspace{\ensuremath{norm}}\xspace{\ensuremath{norm}}\xspace{\ensuremath{norm}}\xspace{\ensuremath{norm}}\xspace{\ensuremath{norm}}\xspace{\ensuremath{norm}}\xspace{\ensuremath{norm}}\xspace{\ensuremath{norm}}\xspace{\ensuremath{norm}}\xspace{\ensuremath{n$
- Placing temperature sensor(Thermistor) close to Crystal blank in one airtight housing can detect more precise crystal blank temperature. Improvement on frequency temperature compensation compared to present Crystal unit.
- Single cavity housing which is ideal to module applications.
- External configuration size is 1.6x1.2mm typ., H0.65 mm Max.
- A surface-mount crystal oscillator. (Reflow soldering is possible.)
- Lead-free. Meets the requirements for re-flow profiling using lead-free solder.



Specifications

Item Model	NX1612SD	
Standard	Standard	Optional
Nominal Frequency (MHz)	26 ≤ F ≤ 76.8	26 ≤ F ≤ 76.8
Overtone Order	Fundamental	Fundamental
Frequency Tolerance (25 ± 3°C)	±10 × 10 ⁻⁶	±10 × 10 ⁻⁶
Frequency versus Temperature Characteristics (with reference to +29 °C)	±12 × 10⁻⁵	Please contact us about temp extended case, *1
Operating Temperature Range (°C)	-30 to +85	Please contact us about temp extended case, *1
Storage Temperature Range (°C)	-40 to +105	-40 to +105
Equivalent Series Resistance	Refer to *2	Refer to *2
Level of Drive (µW)	10 (Max. 100)	10 (Max. 100)
Load Capacitance (pF)	8	6 to 18
Frequency Aging (+25°C)		Max. ±3 × 10 ⁻⁶ / year *1
Specifications Number	STD-CTI-2	Refer to *3

Please specify the model name, frequency, and specification number when you order products.

For futher questions regarding specifications, please feel free to contact us.

*1 If you have any other requests, NDK will study it.

- *3 Ordering information: Overtone Order Fundamental / 3rd Overtone, the Operating Temperature Range, Frequency versus Temperature Characteristics, Frequency Tolerance, and Load Capacitance.
 - Ex. Model, Frequency (38.400000MHz 6digits), S1:Fundamental or S3:3rd Overtone
 - Operating Temperature Range (-30 to +85°C) Frequency versus Temperature Characteristics (±12×10-6)
 - Frequency Tolerance (±12×10⁻⁶) Load Capacitance (7pF)
 - NX1612SD
 - 38.400000MHz
 - S1-3085-12-12-7

Dimensions





#2: Thermistor and GND (Connection with cover) #4: Thermistor

Land pattern (Recommended)



*2 Equivalent Series Resistance

Nominal Frequency (MHz)	Equivalent Series Resistance Max. (Ω)
26 ≤ F < 38.4	80
38.4 ≤ F ≤ 76.8	50

Resistance (R25)	100k Ω ± 1 %
B-Constant (B25-50)	4250K ± 1 %



NX2016SF

For Mobile Communications

Features

Crystal Unit with built-in Thermistor construction.

- Minimize circuit design space by combining crystal unit into one component.
- (Presently, Crystal unit and temperature sensor is mounted in one board separately.)
- Placing temperature sensor(Thermistor) close to Crystal blank in one airtight housing can detect more precise crystal blank temperature. Improvement on frequency temperature compensation compared to present Crystal unit.
- Single cavity housing which is ideal to module applications.
- External configuration size is 2.0x1.6mm typ., H0.65 mm Max.
- A surface-mount crystal oscillator. (Reflow soldering is possible.)
- Lead-free. Meets the requirements for re-flow profiling using lead-free solder.



Specifications

Item Model	NX2016SF	
Standard	Standard	Optional
Nominal Frequency (MHz)	19.2 ≤ F ≤ 52	19.2 ≤ F ≤ 52
Overtone Order	Fundamental	Fundamental
Frequency Tolerance (25 ± 3°C)	±10 × 10 ⁻⁶	±10 × 10 ⁻⁶
Frequency versus Temperature Characteristics (with reference to +32 °C)	±12 × 10⁻⁵	Please contact us about temp extended case, *1
Operating Temperature Range (°C)	-30 to +85	Please contact us about temp extended case, *1
Storage Temperature Range (°C)	-40 to +105	-40 to +105
Equivalent Series Resistance	Refer to *2	Refer to *2
Level of Drive (µW)	10 (Max. 100)	10 (Max. 100)
Load Capacitance (pF)	7	6 to 18
Frequency Aging (+25°C)		Max. ±3 × 10 ⁻⁶ / year *1
Specifications Number	STD-CTZ-1	Refer to *3

Please specify the model name, frequency, and specification number when you order products.

For futher questions regarding specifications, please feel free to contact us.

*1 If you have any other requests, NDK will study it.

- *3 Ordering information: Overtone Order Fundamental / 3rd Overtone, the Operating Temperature Range, Frequency versus Temperature Characteristics, Frequency Tolerance, and Load Capacitance.
 - Ex. Model, Frequency (38.400000MHz 6digits), S1:Fundamental or S3:3rd Overtone

- Operating Temperature Range (-30 to +85°C) - Frequency versus Temperature Characteristics (±12×10⁻⁶)

- Frequency Tolerance (±12×10⁻⁶) - Load Capacitance (7pF)

NX2016SF

S1-3085-12-12-7

Dimensions



*2 Equivalent Series Resistance

Nominal Frequency (MHz)	Equivalent Series Resistance Max. (Ω)
19.2 ≤ F < 24	80
24 ≤ F ≤ 52	60

	•
Resistance (R25)	100k Ω ± 1 %
B-Constant (B25-50)	4250K ± 1 %

^{38.400000}MHz



NX2520SG

For Mobile Communications

Features

Crystal Unit with built-in Thermistor construction.

- Minimize circuit design space by combining crystal unit into one component. (Presently, Crystal unit and temperature sensor is mounted in one board separately.)
- Placing temperature sensor(Thermistor) close to Crystal blank in one airtight housing can detect more precise crystal blank temperature. Improvement on frequency temperature compensation compared to present Crystal unit.
- Single cavity housing which is ideal to module applications.
- Lead-free. Meets the requirements for re-flow profiling using lead-free solder.



Pb Free RoHS Compliant Directive 2011/65/EU

Specifications

Item Model	NX2520SG		
Standard	Standard	Optional	
Nominal Frequency (MHz)	19.2 ≤ F ≤ 54	19.2 ≤ F ≤ 54	
Overtone Order	Fundamental	Fundamental	
Frequency Tolerance (30 ± 3°C)	±10 × 10 ⁻⁶	±10 × 10 ⁻⁶	
Frequency versus Temperature Characteristics (with reference to +30 °C)	±12 × 10⁻ ⁶	Please contact us about temp extended case, *1	
Operating Temperature Range (°C)	-30 to +85	Please contact us about temp extended case, *1	
Storage Temperature Range (°C)	-40 to +105	-40 to +105	
Equivalent Series Resistance	Refer to *2	Refer to *2	
Level of Drive (µW)	10 (Max. 100)	10 (Max. 100)	
Load Capacitance (pF)	7	6 to 18	
Frequency Aging (+25°C)		Max. ±3 × 10 ⁻⁶ / year *1	
Specifications Number	STD-CTX-1	Refer to *3	
Please specify the model name frequency and specification number when you order products			

Please specify the model name, frequency, and specification number when you order products.

For futher questions regarding specifications, please feel free to contact us.

*1 If you have any other requests, NDK will study it.

*3 Ordering information: Overtone Order Fundamental / 3rd Overtone, the Operating Temperature Range, Frequency versus Temperature Characteristics, Frequency Tolerance, and Load Capacitance.

Ex. Model, Frequency (38.400000MHz 6digits), S1:Fundamental or S3:3rd Overtone

- Operating Temperature Range (-30 to +85°C) - Frequency versus Temperature Characteristics (±12×10⁻⁶)

- Frequency Tolerance (±12×10⁻⁶) - Load Capacitance (7pF)

NX2520SG

38.400000MHz

S1-3085-12-12-7



*2 Equivalent Series Resistan	ce
-------------------------------	----

Nominal Frequency (MHz)	Equivalent Series Resistance Max. (Ω)
19.2 ≤ F < 20	70
20 ≤ F < 40	50
40 ≤ F ≤ 54	40

Resistance (R25)	100k Ω ± 1 %
B-Constant (B25-50)	4250K ± 1 %

NX2016SF

For Automotive

Features

Crystal Unit with built-in Thermistor construction for automotive.

- Placing temperature sensor(Thermistor) close to Crystal blank in one airtight housing can detect more precise crystal blank temperature. Improvement on frequency temperature compensation compared to present Crystal unit.
- It is ideal for applications such as vehicle communication equipment and car navigation systems.
- Meets the requirements for re-flow profiling using lead-free solder.
- Conforms to AEC-Q200.



Specifications

Item Model	NX2016SF	
Standard	Standard	Optional
Nominal Frequency (MHz)	19.2 ≤ F ≤ 55.2	19.2 ≤ F ≤ 55.2
Overtone Order	Fundamental	Fundamental
Frequency Tolerance (25°C)	±10 × 10 ⁻⁶	±10 × 10 ⁻⁶
Frequency versus Temperature Characteristics (with reference to +25 °C)	±25 × 10⁻ ⁶	Please contact us about temp extended case, *1
Operating Temperature Range (°C)	-40 to +105	Please contact us about temp extended case, *1
Storage Temperature Range (°C)	-40 to +105	-40 to +105
Equivalent Series Resistance	Refer to *2	Refer to *2
Level of Drive (µW)	10 (Max. 100)	10 (Max. 100)
Load Capacitance (pF)	7	6 to 18
Frequency Aging (+25°C)		Max. ±3 × 10 ⁻⁶ / year *1
Specifications Number		Refer to *3

Please specify the model name, frequency, and specification number when you order products.

For futher questions regarding specifications, please feel free to contact us.

*1 If you have any other requests, NDK will study it.

- *3 Ordering information: Overtone Order Fundamental / 3rd Overtone, the Operating Temperature Range, Frequency versus Temperature Characteristics, Frequency Tolerance, and Load Capacitance.
 - Ex. Model, Frequency (38.400000MHz 6digits), S1:Fundamental or S3:3rd Overtone
 - Operating Temperature Range (-40 to +105°C) Frequency versus Temperature Characteristics (±25×10⁻⁶)
 - Frequency Tolerance (±12×10-6) Load Capacitance (7pF)
 - NX2016SF
 - 38.400000MHz
 - S1-40105-25-12-7

Dimensions



*2 Equivalent Series Resistance

Nominal Frequency (MHz)	Equivalent Series Resistance Max. (Ω)
19.2 ≤ F < 20	70
20 ≤ F < 40	50
40 ≤ F ≤ 55.2	40

Resistance (R25)	100k Ω ± 1 %
B-Constant (B25-50)	4250K ± 1 %

NX1008AA

For OA / AV / Short-range Wireless

Features

- Ultra compact and thin surface-mount type crystal unit.
- Ultra compact and thin (Typ. $1.0 \times 0.8 \times H : 0.30$ mm).
- Highly reliable crystal unit.
- A product with characteristics best suited for ultra compact Wireless LAN and Bluetooth.(For Short-range Wireless)
- A surface-mount crystal oscillator. (Reflow soldering is possible.)
- Lead-free. Meets the requirements for re-flow profiling using lead-free solder.





Specifications

Item Model	NX1008AA		
Standard	Standard		Optional
Nominal Frequency (MHz)	32 ≤ F < 60	60 ≤ F ≤ 80	32 ≤ F ≤ 80
Overtone Order	Funda	mental	Fundamental
Frequency Tolerance (25 ±3 °C)	±10 × 10 ⁻⁶		±10 × 10 ⁻⁶
Frequency versus Temperature Characteristics (with reference to +25 °C)	±10 × 10 ⁻⁶	±15 × 10⁻6	$\pm 25 \times 10^{-6}$ (Temp extended case, *1)
Operating Temperature Range (°C)	-30 to +85		-40 to +85 *1
Storage Temperature Range (°C)	-40 to +85		-40 to +85
Equivalent Series Resistance	Refer to *2		Refer to *2
Level of Drive (µW)	10 (Max. 100)		10 (Max. 100)
Load Capacitance (pF)	8		6 to 12
Frequency Aging (+25°C)			Max. ±3 × 10⁻⁶ / year *1
Specifications Number	STD-CIY-1		Refer to *3

Please specify the model name, frequency, and specification number when you order products.

For futher questions regarding specifications, please feel free to contact us.

*1 If you have any other requests, NDK will study it.

*3 Ordering information: Overtone Order Fundamental / 3rd Overtone, the Operating Temperature Range, Frequency versus Temperature Characteristics, Frequency Tolerance, and Load Capacitance.

Ex. Model, Frequency (38.400000MHz 6digits), S1:Fundamental or S3:3rd Overtone

- Operating Temperature Range (-30 to +85°C) - Frequency versus Temperature Characteristics (±12×10⁻⁶)

- Frequency Tolerance (±12×10-6) - Load Capacitance (7pF)

NX1008AA

38.400000MHz

S1-3085-12-12-7

Dimensions



*2 Equivalent Series Resistance

Nominal Frequency (MHz)	Equivalent Series Resistance Max. (Ω)
32 ≤ F < 37.4	150
37.4 ≤ F < 48	80
48 ≤ F ≤ 80	60

If you have any other requests,NDK will study it.





For OA / AV / Short-range Wireless

Features

- Ultra compact and thin surface-mount type crystal unit.
- Ultra compact and thin (Typ. 1.2 × 1.0 × Typ. 0.25 , H : 0.30mm)
- Highly reliable crystal unit.
- A product with characteristics best suited for ultra compact Wireless LAN and Bluetooth.(For Short-range Wireless)
- A surface-mount crystal oscillator. (Reflow soldering is possible.)
- Lead-free. Meets the requirements for re-flow profiling using lead-free solder.



Specifications

Item Model	NX1210AB	
Standard	Standard	Optional
Nominal Frequency (MHz)	26 ≤ F ≤ 52	26 ≤ F ≤ 80
Overtone Order	Fundamental	Fundamental
Frequency Tolerance (25 ±3 °C)	±10 × 10 ⁻⁶	±10 × 10 ⁻⁶
Frequency versus Temperature Characteristics (with reference to +25 °C)	±15 × 10⁻⁵	±25 × 10 ⁻⁶ (Temp extended case, *1)
Operating Temperature Range (°C)	-30 to +85	-40 to +85 *1
Storage Temperature Range (°C)	-40 to +85	-40 to +85
Equivalent Series Resistance	Refer to *2	Refer to *3
Level of Drive (µW)	10 (Max. 100)	10 (Max. 100)
Load Capacitance (pF)	8	6 to 12
Frequency Aging (+25°C)		Max. ±3 × 10⁻⁶ / year *1
Specifications Number	STD-CIX-1	Refer to *3

Free

RoHS Compliant

Directive 2011/65/EU Directive (EU) 2015/86

Please specify the model name, frequency, and specification number when you order products.

For futher questions regarding specifications, please feel free to contact us.

*1 If you have any other requests, NDK will study it.

*3 Ordering information: Overtone Order Fundamental / 3rd Overtone, the Operating Temperature Range, Frequency versus Temperature Characteristics, Frequency Tolerance, and Load Capacitance.

- Ex. Model, Frequency (38.400000MHz 6digits), S1:Fundamental or S3:3rd Overtone
 - Operating Temperature Range (-30 to +85°C) Frequency versus Temperature Characteristics (±12×10-6)

- Frequency Tolerance (±12×10-6) - Load Capacitance (7pF)

NX1210AB

38.400000MHz

S1-3085-12-12-7

Dimensions



*2 Equivalent Series Resistance

Nominal Frequency (MHz)	Equivalent Series Resistance Max. (Ω)
26 ≤ F < 32	150
32 ≤ F < 40	100
40 ≤ F ≤ 52	60

*3 Equivalent Series Resistance

Nominal Frequency (MHz)	Equivalent Series Resistance Max. (Ω)
26 ≤ F < 32	150
32 ≤ F < 40	100
40 ≤ F ≤ 52	80
52 < F ≤ 80	60



NX1612SA

For OA / AV / Short-range Wireless

Features

- A small and thin surface-mount type crystal unit.
- Ideal for Wearable device and Short-range Wireless module.
- Ultra compact and thin (Typ. 1.6 × 1.2 × 0.3 mm)
- · Lead-free. Meets the requirements for re-flow profiling using lead-free solder.



Specifications

Item Model	NX1612SA	
Standard	Standard	Optional
Nominal Frequency (MHz)	24 ≤ F ≤ 80	24 ≤ F ≤ 80
Overtone Order	Fundamental	Fundamental
Frequency Tolerance (25 ±3 °C)	±10 × 10 ⁻⁶	±10 × 10 ⁻⁶
Frequency versus Temperature Characteristics (with reference to +25 °C)	±15 × 10⁻⁵	±25 × 10⁻⁵ (Temp extended case, *1)
Operating Temperature Range (°C)	-30 to +85	-40 to +85 *1
Storage Temperature Range (°C)	-40 to +85	-40 to +85
Equivalent Series Resistance	Refer to *2	Refer to *2
Level of Drive (µW)	10 (Max. 100)	10 (Max. 100)
Load Capacitance (pF)	8	6 to 18
Frequency Aging		Max. ±3 × 10 ⁻⁶ / year *1
Specifications Number	STD-CIS-3	Refer to *3

Pb Fre<u>e</u>

RoHS Compliant ve 2011/6 e (EU) 20

Please specify the model name, frequency, and specification number when you order products.

For futher questions regarding specifications, please feel free to contact us.

*1 If you have any other requests, NDK will study it.

*3 Ordering information: Overtone Order Fundamental / 3rd Overtone, the Operating Temperature Range, Frequency versus Temperature Characteristics, Frequency Tolerance, and Load Capacitance.

- Ex. Model, Frequency (38.400000MHz 6digits), S1:Fundamental or S3:3rd Overtone
 - Operating Temperature Range (-30 to +85°C) Frequency versus Temperature Characteristics (±12×10⁻⁶)
 - Frequency Tolerance (±12×10⁻⁶) Load Capacitance (7pF)
 - NX1612SA
 - 38.400000MHz

S1-3085-12-12-7 Dimensions mm Terminal land connections (TOP VIEW) 1.2±0. COVER #3 нΟн 1.6±0.1 #1 #2 0.30±0.05 TERMINAL Cover #1, #3 : X' tal #2, #4 : GND (Connection with cover) (Metal) Land pattern (Recommended) Base (Alumina Ceramics) Ferminal Au plating finish Ni pre-plating on 0.65 0.45 ± 0.05 ŝ metalize 0 45±0.05 0.75 #4 1.05 L - #3 9.4 0.55±0.05 0.55±0.05

*2 Equivalent Series Resistance

Nominal Frequency (MHz)	Equivalent Series Resistance Max. (Ω)
24 ≤ F < 32	150
32 ≤ F < 38	100
38 ≤ F ≤ 80	80

NX1612SA

Features

- A small and thin surface-mount type crystal unit for automotive.
- •Ultra compact and thin. (1.6 × 1.2 × 0.3 mm)
- •Stable start-up characteristics even under extremely severe environmental conditions.
- •Excellent environmental characteristics, including heat, vibration and shock resistance.
- •Lead-free. Meets the requirements for re-flow profiling using lead-free solder.
- •Conforms to AEC-Q200



27:000 57:000 57:000

Specifications

Item Model	NX1612SA	
Standard	Standard	Optional
Nominal Frequency (MHz)	24 ≤ F ≤ 80	24 ≤ F ≤ 80
Overtone Order	Fundamental	Fundamental
Frequency Tolerance (25 ±3 °C)	±15 × 10 ⁻⁶	±15 × 10 ⁻⁶
Frequency versus Temperature Characteristics (with reference to +25 °C)	±50 × 10⁻ ⁶	±50 × 10 ⁻⁶ (Temp extended case, *1)
Operating Temperature Range (°C)	-40 to +125	-40 to +125
Storage Temperature Range (°C)	-40 to +125	-40 to +125
Equivalent Series Resistance	Refer to *2	Refer to *2
Level of Drive (µW)	10 (Max. 200)	10 (Max. 200)
Load Capacitance (pF)	8	6 to 18
Frequency Aging (+25°C)		Max. ±3 × 10⁻⁵/year *1
Specifications Number	STD-CIC-1	Refer to *3

Please specify the model name, frequency, and specification number when you order products.

For futher questions regarding specifications, please feel free to contact us.

*1 If you have any other requests, NDK will study it.

*3 Ordering information: Overtone Order Fundamental / 3rd Overtone, the Operating Temperature Range, Frequency versus Temperature Characteristics, Frequency Tolerance, and Load Capacitance.

Ex. Model, Frequency (38.400000MHz 6digits), S1:Fundamental or S3:3rd Overtone

- Operating Temperature Range (-40 to +125°C) - Frequency versus Temperature Characteristics (±50×10⁻⁶)

- Frequency Tolerance (±15×10⁻⁶) Load Capacitance (7pF)
- NX1612SA
- 38.400000MHz

S1-40125-50-15-7





*2 Equivalent Series Resistance

Nominal Frequency (MHz)	Equivalent Series Resistance Max. (Ω)
24 ≤ F < 32	150
32 ≤ F < 38	100
38 ≤ F ≤ 80	80

If you have any other requests,NDK will study it.





NX2016SA For OA / AV/ Short-range Wireless

Features

A small and thin surface-mount type crystal unit, especially suited for small-sizing requirements.

- •Ultra compact and thin. (2.0 \times 1.6 \times 0.45 mm)
- •Excellent environmental characteristics, including heat and shock resistance.
- •Excellent electrical performance, ideal for OA (office automation), AV(audiovisual), Bluetooth and Wireless LAN applications.
- •Lead-free. Meets the requirements for re-flow profiling using leadfree solder.





Specifications

Item Model	NX2016SA		
Standard	Star	ndard	Optional
Nominal Frequency (MHz)	16 ≤	F ≤ 80	16 ≤ F ≤ 80
Overtone Order	Fundamental		Fundamental
Frequency Tolerance (25 ±3 °C)	±10 × 10 ⁻⁶		±10 × 10 ⁻⁶
Frequency versus Temperature Characteristics (with reference to +25 °C)	±25 × 10⁻⁵	±15 × 10⁻6	±25 × 10 ⁻⁶ (Temp extended case, *1)
Operating Temperature Range (°C)	-40 to +85	-10 to +75	-40 to +85 *1
Storage Temperature Range (°C)	-40 to +85		-40 to +85
Equivalent Series Resistance	Refer to *2		Refer to *2
Level of Drive (µW)	10 (Max. 100)		10 (Max. 100)
Load Capacitance (pF)	8		6 to 18
Frequency Aging (+25°C)			Max. ±3 × 10 ⁻⁶ / year *1
Specifications Number	STD-CZS-7	STD-CZS-6	Refer to *3

Please specify the model name, frequency, and specification number when you order products.

For futher questions regarding specifications, please feel free to contact us.

*1 If you have any other requests, NDK will study it.

- *3 Ordering information: Overtone Order Fundamental / 3rd Overtone, the Operating Temperature Range, Frequency versus Temperature Characteristics, Frequency Tolerance, and Load Capacitance.
 - Ex. Model, Frequency (38.400000MHz 6digits), S1:Fundamental or S3:3rd Overtone
 - Operating Temperature Range (-40 to +85°C) Frequency versus Temperature Characteristics (±25×10-6)

- Frequency Tolerance (±12×10⁻⁶) - Load Capacitance (7pF)

- NX2016SA
- 38.400000MHz

S1-4085-25-12-7

Dimensions



*2 Equivalent Series Resistance

Nominal Frequency (MHz)	Equivalent Series Resistance Max. (Ω)
16 ≤ F < 18	200
18 ≤ F < 20	150
20 ≤ F < 24	100
24 ≤ F < 26	80
26 ≤ F < 40	60
40 ≤ F ≤ 80	50

If you have any other requests,NDK will study it.

NX2016GC

RoHS Compliant

Directive 2011/65/EU Directive (EU) 2015/863

Features

High reliability small surface-mount type crystal unit for automotive.

- •High resistance to solder cracking.
- •Ultra compact and thin. (2.0 x 1.6 x 0.7mm)
- •Stable start-up characteristics even under extremely severe environmental conditions.
- •Excellent environment-resistant performance, including heat, vibration and shock resistance.
- •Meets the requirements for re-flow profiling using lead-free solder.
- •Conforms to AEC-Q200.

Specifications

Item Model	NX20	16GC
Standard	Standard	Optional
Nominal Frequency (MHz)	16 ≤ F ≤ 50	16 ≤ F ≤ 50
Overtone Order	Fundamental	Fundamental
Frequency Tolerance (25 ±3 °C)	±50 × 10 ⁻⁶	±50 × 10 ⁻⁶
Frequency versus Temperature Characteristics (with reference to +25 °C)	±150 × 10⁻6	±150 × 10⁻⁰
Operating Temperature Range (°C)	-40 to +150	-40 to +150
Storage Temperature Range (°C)	-40 to +150	-40 to +150
Equivalent Series Resistance	Refer to *1	Refer to *1
Level of Drive (µW)	10 (Max. 200)	10 (Max. 200)
Load Capacitance (pF)	8	6 to 18
Frequency Aging (+25°C)		Max. ±10 × 10⁻⁶ / year *2
Specifications Number	STD-CZA-1	Refer to *3

Please specify the model name, frequency, and specification number when you order products.

For futher questions regarding specifications, please feel free to contact us.

*2 If you have any other requests, NDK will study it.

- *3 Ordering information: Overtone Order Fundamental / 3rd Overtone, the Operating Temperature Range, Frequency versus Temperature Characteristics, Frequency Tolerance, and Load Capacitance.
 - Ex. Model, Frequency (38.400000MHz 6digits), S1:Fundamental or S3:3rd Overtone
 - Operating Temperature Range (-40 to +150°C) Frequency versus Temperature Characteristics (±150×10⁻⁶)
 - Frequency Tolerance (±50×10⁻⁶) Load Capacitance (7pF)
 - NX2016GC
 - 38.400000MHz
 - S1-40150-150-50-7

Dimensions



*1 Equivalent Series Resistance

Nominal Frequency (MHz)	Equivalent Series Resistance Max. (Ω)
16 ≤ F < 20	300
20 ≤ F < 22	220
22 ≤ F < 26	180
26 ≤ F ≤ 50	120

If you have any other requests,NDK will study it.

NX2016SA

Pb

Free

Directive 2011/65/EU irective (EU) 2015/86

Features

- A small and thin surface-mount type crystal unit for automotive.
- Ultra compact and thin. (2.0 × 1.6 × 0.45 mm)
- Stable start-up characteristics even under extremely severe environmental conditions.
- Excellent environmental characteristics, including heat, vibration and shock resistance.
- · Lead-free. Meets the requirements for re-flow profiling using lead-free solder **RoHS** Compliant
- Conforms to AEC-Q200.

Specifications

Item Model	NX2016SA	
Standard	Standard	Optional
Nominal Frequency (MHz)	16 ≤ F ≤ 80	16 ≤ F ≤ 80
Overtone Order	Fundamental	Fundamental
Frequency Tolerance (25 ±3 °C)	±15 × 10 ⁻⁶	±15 × 10 ⁻⁶
Frequency versus Temperature Characteristics (with reference to +25 °C)	±50 × 10 ⁻⁶	±50 × 10 ⁻⁶
Operating Temperature Range (°C)	-40 to +125	-40 to +125
Storage Temperature Range (°C)	-40 to +125	-40 to +125
Equivalent Series Resistance	Refer to *1	Refer to *1
Level of Drive (µW)	10 (Max. 200)	10 (Max. 200)
Load Capacitance (pF)	8	6 to 18
Frequency Aging (+25°C)		Max. ±3 × 10⁻⁶ / year *2
Specifications Number	STD-CZS-3	Refer to *3

Please specify the model name frequency and specification number when you order products.

For futher questions regarding specifications, please feel free to contact us.

*2 If you have any other requests, NDK will study it.

- *3 Ordering information: Overtone Order Fundamental / 3rd Overtone, the Operating Temperature Range, Frequency versus Temperature Characteristics, Frequency Tolerance, and Load Capacitance.
 - Ex. Model, Frequency (38.400000MHz 6digits), S1:Fundamental or S3:3rd Overtone
 - Operating Temperature Range (-40 to +125°C) Frequency versus Temperature Characteristics (±50×10⁻⁶)
 - Frequency Tolerance (±15×10⁻⁶) Load Capacitance (7pF)
 - NX2016SA
 - 38.400000MHz
 - S1-40125-50-15-7

Dimensions



*1 Equivalent Series Resistance

1	•	
	Nominal Frequency (MHz)	Equivalent Series Resistance Max. (Ω)
	16 ≤ F < 20	200
	20 ≤ F < 24	100
	24 ≤ F < 26	80
	26 ≤ F < 40	60
	40 ≤ F ≤ 80	50

If you have any other requests,NDK will study it.







NX2520SA For OA / AV Mobile Communications/ Short-range Wireless

RoHS Compliant

ctive 2011/65/EU ive (EU) 2015/86

Dire

Features

Ideal for such as Bluetooth, Wi-Fi, smartphone and tablet pc.

•Compact and thin. (2.5 × 2.0 × 0.50 mm typ.)

- •Excellent environmental characteristics, including heat and shock resistance.
- •Lead-free. Meets the requirements for re-flow profiling using lead-free solder.



Specifications

~			
Item Model	NX2520SA		
Standard	Stan	dard	Optional
Nominal Frequency (MHz)	16 ≤ F ≤ 80	16 ≤ F ≤ 54	16 ≤ F ≤ 80
Overtone Order		Fundamental	
Frequency Tolerance (25 ±3 °C)	±15 × 10 ⁻⁶ ±10 × 10 ⁻⁶		±8×10 ⁻⁶ (16 ≤ F ≤ 40MHz) ±12×10 ⁻⁶ (40 < F ≤ 80MHz)
Frequency versus Temperature Characteristics (with reference to +25 °C)	±25 × 10⁻ ⁶	±10 × 10 ⁻⁶	±10 × 10 ^{–6} (Temp extended case, *1)
Operating Temperature Range(°C)	-40 to +85	–20 to +75	-20 to +75 (-40 to +85 °C Extended)
Storage Temperature Range (°C)	-40 to +85		-40 to +125
Equivalent Series Resistance	Refer to *2	Refer to *3	Refer to *2
Level of Drive (µW)	10 (Max. 100)		10 (Max. 200) *1
Load Capacitance (pF)	8		6 to 32
Frequency Aging (+25 °C)			Max. ±3×10 ⁻⁶ / year *1
Specifications Number	STD-CSW-6	STD-CSX-1	Refer to *4

Ph

Free

Please specify the model name, frequency, and specification number when you order products.

For further questions regarding specifications, please feel free to contact us.

*1 If you have any other requests, NDK will study it.

*4 Ordering information: Overtone Order Fundamental / 3rd Overtone, the Operating Temperature Range, Frequency versus Temperature Characteristics, Frequency Tolerance, and Load Capacitance.

Ex. Model, Frequency (24.000000MHz 6digits), S1: Fundamental or S3 : 3rd overtone

- Operating Temperature Range (-40 to +85°C) - Frequency versus Temperature Characteristics (±25 × 10⁻⁶)

- Frequency Tolerance $(\pm 10 \times 10^{-6})$ - Load Capacitance (8pF)

NX2520SA

24.000000MHz

S1-4085-25-10-8

Dimensions



*2 Equivalent Series Resistance

Nominal Frequency (MHz)	Equivalent Series Resistance Max. (Ω)
16 ≤ F < 20	80
20 ≤ F < 30	60
30 ≤ F < 35	50
35 ≤ F ≤ 80	40

If you have any other requests, NDK will study it.

*3 Equivalent Series Resistance

Nominal Frequency (MHz)	Equivalent Series Resistance Max. (Ω)
16 ≤ F < 20	80
20 ≤ F < 30	60
30 ≤ F < 35	50
35 ≤ F ≤ 54	40

If you have any other requests, NDK will study it.

NIHON DEMPA KOGYO CO., LTD.



NX3225SA For OA / AV Mobile Communications/ Short-range Wireless

Pb Free

RoHS Compliant Directive 2011/65/EU Directive (EU) 2015/863

Features

- Ideal for such as bluetooth, Wifi, smartphone and tablet pc.
- •Compact and thin. (3.2 × 2.5 × 0.55 mm typ.)
- Excellent environmental characteristics, including heat and shock resistance.
- •Lead-free. Meets the requirements for re-flow profiling using lead-free solder.



Specifications

Item Model	NX3225SA			
Standard		Standard		Optional
Nominal Frequency (MHz)	12 ≤ F ≤ 64	16 ≤ F ≤ 54	40 ≤ F ≤150	12 ≤ F ≤ 64
Overtone Order	Fundamental	Fundamental	3rd overtone	Fundamental
Frequency Tolerance (25 ±3 °C)	±15 × 10⁻6	±10 × 10 ⁻⁶	±20 × 10⁻6	±10 × 10 ⁻⁶
Frequency versus Temperature Characteristics (with reference to +25 °C)	±25 × 10⁻⁵	±10 × 10 ⁻⁶	±25 × 10 ⁻⁶	±25 × 10 ⁻⁶ (Temp extended case, *1)
Operating Temperature Range (°C)	-40 to +85	-20 to +75	-40 to +85	-40 to +85 *1
Storage Temperature Range	-40 to +85		-40 to +85	
Equivalent Series Resistance	Refer to *2	Refer to *3	Refer to *4	Refer to *1
Level of Drive (µW)	10 (Max. 200)		10 (Max. 200)	
Load Capacitance (pF)	8	10	Series resonance	6 to 32
Frequency Aging (+25°C)			Max. ±3 × 10 ⁻⁶ / year *1	
Specifications Number	STD-CSR-6	STD-CSQ-1	STD-CSR-7	Refer to *5

Please specify the model name, frequency, and specification number when you order products.

For further questions regarding specifications, please feel free to contact us.

*1 If you have any other requests, NDK will study it.

*5 Ordering information: Overtone Order Fundamental / 3rd Overtone, the Operating Temperature Range, Frequency versus Temperature Characteristics, Frequency Tolerance, and Load Capacitance.

Ex. Model, Frequency (24.000000MHz 6digits), S1: Fundamental or S3 : 3rd overtone

- Operating Temperature Range (-40 to +85°C) - Frequency versus Temperature Characteristics (±25 × 10⁻⁶)

- Frequency Tolerance $(\pm 10 \times 10^{-6})$ - Load Capacitance (8pF)

NX3225SA

24.000000MHz

S1-4085-25-10-8

Dimensions





	Overtone Order	Nominal Frequency (MHz)	Equivalent Series Resistance Max. (Ω)
		12 ≤ F < 13	100
*2 Fundament	Fundamental	13 ≤ F < 20	80
		20 ≤ F ≤ 64	50
*2	*3 Fundamental	16 ≤ F < 20	80
3		20 ≤ F ≤ 54	50
*4	3rd overtone	40 ≤ F < 100	140
		100 ≤ F ≤ 150	100

Equivalent Series Resistance

If you have any other requests,NDK will study it.

Eana pattorn (resseringerasa

NX3225GA

RoHS Compliant Directive 2011/65/EU Directive (EU) 2015/863

Features

A small surface-mount type crystal unit, especially suited for small-sizing requirements.

- •Compact and thin. (3.2 x 2.5 x 0.75 mm typ.)
- •Excellent environmental characteristics, including heat and shock resistance.
- •Excellent electrical performance for OA (office automation) and AV (audiovisual) applications.
- •Meets the requirements for re-flow profiling using lead-free solder.



Specifications

Item Model	NX3225GA	
Standard	Standard	Optional
Nominal Frequency (MHz)	9.840 ≤ F ≤ 50	9.840 ≤ F ≤ 50
Overtone Order	Fundamental	Fundamental
Frequency Tolerance (25 ±3 °C)	±20 × 10 ⁻⁶	±20 × 10 ⁻⁶
Frequency versus Temperature Characteristics (with reference to +25 °C)	±30 × 10 ⁻⁶	±30 × 10 ^{-₀} (Temp extended case, *1)
Operating Temperature Range (°C)	-40 to +85	-40 to +85 *1
Storage Temperature Range (°C)	-40 to +85	-40 to +85
Equivalent Series Resistance	Refer to *2	Refer to *2
Level of Drive (µW)	10 (Max. 200)	10 (Max. 200)
Load Capacitance (pF)	8	6 to 32
Frequency Aging (+25 °C)		Max. ±10 × 10⁻⁶ / year *1
Specifications Number	STD-CRG-2	Refer to *3

Please specify the model name, frequency, and specification number when you order products.

For futher questions regarding specifications, please feel free to contact us.

*1 If you have any other requests, NDK will study it.

- *3 Ordering information: Overtone Order Fundamental / 3rd Overtone, the Operating Temperature Range, Frequency versus Temperature Characteristics, Frequency Tolerance, and Load Capacitance.
 - Ex. Model, Frequency (38.400000MHz 6digits), S1:Fundamental or S3:3rd Overtone
 - Operating Temperature Range (-40 to +85°C) Frequency versus Temperature Characteristics (±30×10⁻⁶)
 - Frequency Tolerance (±20×10⁻⁶) Load Capacitance (8pF)
 - NX3225GA
 - 38.400000MHz
 - S1-4085-30-20-8

Dimensions

2.5±0.1

75±0.15





mm





*2 Equivalent Series Resistance

Nominal Frequency (MHz)	Equivalent Series Resistance Max. (Ω)
9.840 ≤ F < 12	200
12 ≤ F < 13	100
13 ≤ F < 20	80
20 ≤ F ≤ 50	50

If you have any other requests,NDK will study it.



For OA / AV



For Automotive

Features

- A surface-mount compact crystal unit suitable for automotive.
- •Compact and thin. (3.2 x 2.5 x 0.75 mm typ.)
- •Stable start-up characteristics even under extremely severe environmental conditions.
- •Excellent environment-resistant performance, including heat, vibration and shock resistance.
- •Meets the requirements for re-flow profiling using lead-free solder.
- •Conforms to AEC-Q200.



Specifications

Item Model	NX3225GA		
Standard	Standard	Optional	
Nominal Frequency (MHz)	9.8 ≤ F ≤ 50	9.8 ≤ F ≤ 50	
Overtone Order	Fundamental	Fundamental	
Frequency Tolerance (25 ±3 °C)	±50 × 10 ⁻⁶	±50 × 10 ⁻⁶	
Frequency versus Temperature Characteristics (with reference to +25 °C)	$\pm 150 \times 10^{-6}$	$\pm 150 \times 10^{-6}$	
Operating Temperature Range (°C)	-40 to +150	-40 to +150	
Storage Temperature Range (°C)	-40 to +150	-40 to +150	
Equivalent Series Resistance	Refer to *1	Refer to *1	
Level of Drive (µW)	10 (Max. 200)	10 (Max. 200)	
Load Capacitance (pF)	8	6 to 32	
Frequency Aging (+25°C)		Max. ±10 × 10 ⁻⁶ / year *2	
Specifications Number	STD-CRA-1	Refer to *3	

NX3225GA

Please specify the model name frequency and specification number when you order products.

For futher questions regarding specifications, please feel free to contact us.

*2 If you have any other requests, NDK will study it.

*3 Ordering information: Overtone Order Fundamental / 3rd Overtone, the Operating Temperature Range, Frequency versus Temperature Characteristics, Frequency Tolerance, and Load Capacitance.

mm

#3

- Ex. Model, Frequency (38.400000MHz 6digits), S1:Fundamental or S3:3rd Overtone
- Operating Temperature Range (-40 to +150°C) Frequency versus Temperature Characteristics (±150×10-6)
- Frequency Tolerance (±50×10⁻⁶) Load Capacitance (8pF)
- NX3225GA
- 38.400000MHz

S-40150-150-50-8

Dimensions



*1 Equivalent Series Resistance

Nominal Frequency (MHz)	Equivalent Series Resistance Max. (Ω)
9.8 ≤ F < 12	300
12 ≤ F < 20	120
20 ≤ F ≤ 50	100

If you have any other requests,NDK will study it.

•Compact and thin. (3.2 x 2.5 x 0.75 mm typ.)

• High resistance to solder cracking.

Features

resistance.

*If you required 7.98 to 12MHz, please refer to NX3225GD.

Characteristics, Frequency Tolerance, and Load Capacitance.

Ex. Model, Frequency(38.400000MHz 6digits), S1:Fundamental or S3:3rd Overtone

- Operating Temperature Range (-40 to +150°C) - Frequency versus Temperature Characteristics (±150×10-6)

- Frequency Tolerance (±50×10-6) - Load Capacitance (8pF)

- NX3225GB



Specifications

•Conforms to AEC-Q200.

Item Model	NX3225GB		
Standard	Standard	Optional	
Nominal Frequency (MHz)	12 ≤ F ≤ 50	12 ≤ F ≤ 50	
Overtone Order	Fundamental	Fundamental	
Frequency Tolerance (25 ±3 °C)	±50 × 10 ⁻⁶	±50 × 10 ⁻⁶	
Frequency versus Temperature Characteristics (with reference to +25 $^\circ\text{C}$)	±150 × 10⁻⁰	±150 × 10⁻ ⁶	
Operating Temperature Range (°C)	-40 to +150	-40 to +150	
Storage Temperature Range (°C)	-40 to +150	-40 to +150	
Equivalent Series Resistance	Refer to *1	Refer to *1	
Level of Drive (µW)	10 (Max. 200)	10 (Max. 200)	
Load Capacitance (pF)	8	6 to 32	
Frequency Aging (+25 °C)		Max. ±10 × 10 ⁻⁶ / year *2	
Specifications Number	STD-CRA-2	Refer to *3	

Please specify the model name, frequency, and specification number when you order products.

A small surface-mount type crystal unit, ideal for an engine control CPU clock; delivering the high reliability that is particularly demanded by automotive.

•Stable start-up characteristics even under extremely severe environmental conditions.

For futher questions regarding specifications, please feel free to contact us.

*2 If you have any other requests, NDK will study it.

*3 Ordering information: Overtone Order Fundamental / 3rd Overtone, the Operating Temperature Range, Frequency versus Temperature

- 38.400000MHz
- S1-40150-150-50-8

Dimensions

•Excellent environment-resistant performance, including heat, vibration and shock RoHS Compliant •Meets the requirements for re-flow profiling using lead-free solder. Directive 2011/65/EU Directive (EU) 2015/86

NX3225GB



*1 Equivalent Series Resistance

Nominal Frequency (MHz)	Equivalent Series Resistance Max. (Ω)
12 ≤ F < 20	120
20 ≤ F ≤ 50	100

If you have any other requests,NDK will study it.



NX3225GD

Features

- A small surface-mount type crystal unit, ideal for an engine control CPU clock; delivering the high reliability that is particularly demanded by automotive.
- Compatible with low frequency range starting from 7.98 MHz.
- •Compact and thin. (3.2 x 2.5 x 0.8mm)
- •High resistance to solder cracking.
- Stable start-up characteristics even under extremely severe environmental conditions.
- •Excellent environment-resistant performance, including heat, vibration and shock resistance.
- •Meets the requirements for re-flow profiling using lead-free solder. •Conforms to AEC-Q200.

Specifications

Item Model	NX3225GD		
Standard	Standard	Optional	
Nominal Frequency (MHz)	7.98 ≤ F ≤ 12	7.98 ≤ F ≤ 12	
Overtone Order	Fundamental	Fundamental	
Frequency Tolerance (25 ±3 °C)	±50 × 10 ⁻⁶	±50 × 10 ⁻⁶	
Frequency versus Temperature Characteristics (with reference to +25 $^{\circ}$ C)	±150 × 10 ⁻⁶	±150 × 10 ⁻⁶	
Operating Temperature Range (°C)	-40 to +150	-40 to +150	
Storage Temperature Range (°C)	-40 to +150	-40 to +150	
Equivalent Series Resistance	Refer to *1	Refer to *1	
Level of Drive (µW)	10 (Max. 200)	10 (Max. 200)	
Load Capacitance (pF)	8	6 to 32	
Frequency Aging (+25 °C)		Max. ±10 × 10 ⁻⁶ / year *2	
Specifications Number	STD-CRA-3	Refer to *3	

Please specify the model name, frequency, and specification number when you order products.

For futher questions regarding specifications, please feel free to contact us.

*2 If you have any other requests, NDK will study it.

*3 Ordering information: Overtone Order Fundamental / 3rd Overtone, the Operating Temperature Range, Frequency versus Temperature Characteristics, Frequency Tolerance, and Load Capacitance.

- Ex. Model, Frequency(10.000000MHz 6digits), S1:Fundamental or S3:3rd Overtone
 - Operating Temperature Range (-40 to +150°C) Frequency versus Temperature Characteristics (±150×10⁻⁶)

- Frequency Tolerance (±50×10-6) - Load Capacitance (8pF)

NX3225GD

10.00000MHz

S1-40150-150-50-8

Dimensions



*1 Equivalent Series Resistance

Nominal Frequency (MHz)	Equivalent Series Resistance Max. (Ω)
7.98 ≤ F < 9.8	500
9.8 ≤ F ≤ 12	300

If you have any other requests,NDK will study it.





RoHS Compliant

Directive 2011/65/EU Directive (EU) 2015/863



Features

- A small surface-mount type crystal unit, ideal for automotive applications.
- •With a well established reputation for reliability, this product is best suited for automotive equipment.
- •Stable start-up characteristic even under extremely severe environmental conditions.
- •Excellent environmental characteristics, including heat, vibration and shock Ph resistance.
- •Lead-free. Meets the requirements for re-flow profiling using lead-free solder
- •Conforms to AEC-Q200.

Free **RoHS** Compliant Directive 2011/65/EU Directive (EU) 2015/86

Specifications

Item Model	NX3225SA		
Standard	Standard	Optional	
Nominal Frequency (MHz)	12 ≤ F ≤ 50	12 ≤ F ≤ 50	
Overtone Order	Fundamental	Fundamental	
Frequency Tolerance (25 ±3 °C)	±15 × 10 ⁻⁶	±15 × 10 ⁻⁶	
Frequency versus Temperature Characteristics (with reference to +25 °C)	±50 × 10-6	±50 × 10⁻⁵	
Operating Temperature Range (°C)	-40 to +125	-40 to +125	
Storage Temperature Range (°C)	-40 to +125	-40 to +125	
Equivalent Series Resistance	Refer to *1	Refer to *1	
Level of Drive (µW)	10 (Max. 200)	10 (Max. 200)	
Load Capacitance (pF)	8	6 to 32	
Frequency Aging (+25 °C)		Max. ±3 × 10⁻⁶ / year *2	
Specifications Number	STD-CRS-2	Refer to *3	

Please specify the model name, frequency, and specification number when you order products.

For futher questions regarding specifications, please feel free to contact us.

*2 If you have any other requests, NDK will study it.

*3 Ordering information: Overtone Order Fundamental / 3rd Overtone, the Operating Temperature Range, Frequency versus Temperature Characteristics, Frequency Tolerance, and Load Capacitance.

- Ex. Model, Frequency (38.400000MHz 6digits), S1:Fundamental or S3:3rd Overtone
 - Operating Temperature Range (-40 to +125°C) Frequency versus Temperature Characteristics (±50×10⁻⁶)

- Frequency Tolerance (±15×10⁻⁶) - Load Capacitance (8pF)

NX3225SA

38.400000MHz

S1-40125-50-15-8









*#2 and #4 are connected with a cover.



*1 Equivalent Series Resistance

Nominal Frequency (MHz)	Equivalent Series Resistance Max. (Ω)
12 ≤ F < 20	120
20 ≤ F ≤ 50	100

If you have any other requests,NDK will study it.





Features

A small surface-mount type crystal unit, ideal for the special requirements of automotive, such as TPMS (Tire Pressure Monitoring System). The crystal unit is ideally suited for the clock signal generating source of the transmission unit in a tire wheel that is subject to strong centrifugal force.

- •Compact and thin. (3.2 x 2.5 x 0.6 mm typ.)
- Stable frequency characteristics even with a powerful centrifugal force of 2,000 G, as found in the transmission side of TPMS applications.
- •High resistance to solder cracking.
- •Excellent environmental characteristics, including heat, vibration and shock resistance.
- •Lead-free. Meets the requirements for re-flow profiling using lead-free solder.
- •Conforms to AEC-Q200.

Specifications



Item Model	NX3225SC	
Standard	Standard	Optional
Nominal Frequency (MHz)	9.8433 ≤ F ≤ 50	9.8433 ≤ F ≤ 50
Overtone Order	Fundamental	Fundamental
Frequency Tolerance (25 ±3 °C)	±15 × 10 ⁻⁶	±15 × 10 ⁻⁶
Frequency versus Temperature Characteristics (with reference to +25 $^\circ\text{C}$)	±50 × 10⁻ ⁶	±50 × 10⁻⁵
Operating Temperature Range (°C)	-40 to +125	-40 to +125
Storage Temperature Range (°C)	-40 to +125	-40 to +125
Equivalent Series Resistance	Refer to *1	Refer to *1
Level of Drive (µW)	10 (Max. 200)	10 (Max. 200)
Load Capacitance (pF)	8	6 to 32
Frequency Aging (+25 °C)		Max. ±3 × 10⁻⁶ / year *2
Specifications Number	STD-CRS-1 Refer to *3	

Please specify the model name, frequency, and specification number when you order products.

For futher questions regarding specifications, please feel free to contact us.

*2 If you have any other requests, NDK will study it.

- *3 Ordering information: Overtone Order Fundamental / 3rd Overtone, the Operating Temperature Range, Frequency versus Temperature Characteristics, Frequency Tolerance, and Load Capacitance.
 - Ex. Model, Frequency (38.400000MHz 6digits), S1:Fundamental or S3:3rd Overtone
 - Operating Temperature Range (-40 to +125°C) Frequency versus Temperature Characteristics (±50×10⁻⁶)
 - Frequency Tolerance (±15×10-6) Load Capacitance (8pF)
 - NX3225SC
 - 38.400000MHz
 - S1-40125-50-15-8

Dimensions



*1 Equivalent Series Resistance

Nominal Frequency (MHz)	Equivalent Series Resistance Max. (Ω)
9.8433 ≤ F < 12	300
12 ≤ F < 20	120
20 ≤ F ≤ 50	100
	Nominal Frequency (MHz) $9.8433 \le F < 12$ $12 \le F < 20$ $20 \le F \le 50$

If you have any other requests,NDK will study it.



RoHS Compliant

Features

- Ideal for OA/AV applications and Accessories for a car.
- Compact and thin. (5.0×3.2×1.3mm typ.)
- Supports low frequencies starting from 8 MHz.
- Excellent environmental characteristics, including heat and shock resistance.
- Meets the requirements for re-flow profiling using lead-free solder.



Specifications

Item Model	NX5032GA					
Standard			Standard			Optional
Nominal Frequency (MHz)	8 ≤ F < 10.499	10.5≤F≤ 49.999	8 ≤ F ≤ 10.499	10.5≤F≤ 49.999	50 ≤ F ≤ 55	8 ≤ F ≤ 55
Overtone Order			Fundamental			Fundamental
Frequency Tolerance (25 ±3 °C)	±30 >	< 10 ⁻⁶		±20 × 10 ⁻⁶		±20 × 10⁻6
Frequency versus Temperature Characteristics (with reference to +25 °C)	±50 >	< 10 ^{−6}		±30 × 10 ⁻⁶		±50 × 10⁻⁰
Operating Temperature Range (°C)	-40 t	o +85		-10 to +70		-40 to +85 *3
Storage Temperature Range (°C)	-40 to +125		-40 to +85		-40 to +125	
Equivalent Series Resistance	Refer to *1		Refer to *2		Refer to *1 *2	
Level of Drive (µW)	50 (Max. 500)		50 (Max. 500)			
Load Capacitance (pF)	8		6 to 32			
Frequency Aging (+25 °C)						Max. ±10 × 10⁻⁰ / year *3
Specifications Number	STD-CSK-7	STD-CSK-8	STD-CSK-3	STD-CSK-4	STD-CKW-3	Refer to *4

Please specify the model name, frequency, and specification number when you order products.

For further questions regarding specifications, please feel free to contact us.

*3 If you have any other requests, NDK will study it.

*4 Ordering information: Overtone Order Fundamental / 3rd Overtone, the Operating Temperature Range, Frequency versus Temperature Characteristics, Frequency Tolerance, and Load Capacitance.

Ex. Model, Frequency (24.000000MHz 6digits), S1: Fundamental or S3 : 3rd overtone

- Operating Temperature Range (-40 to +85°C) - Frequency versus Temperature Characteristics (±50 × 10-6)

- Frequency Tolerance $(\pm 20 \times 10^{-6})$ - Load Capacitance (10pF)

NX5032GA

24.000000MHz

S1-4085-50-20-10

Dimensions





mm

Land pattern (Recommended)



*1 Equivalent Series Resistance

Nominal Frequency (MHz)	Equivalent Series Resistance Max. (Ω)
8 ≤ F < 9.5	300
9.5 ≤ F < 10	150
10 ≤ F < 20	120
20 ≤ F < 30	70
30 ≤ F ≤ 49.99	50

If you have any other requests,NDK will study it.

*2 Equivalent Series Resistance

Nominal Frequency (MHz)	Equivalent Series Resistance Max. (Ω)
8 ≤ F < 9.5	300
9.5 ≤ F < 15	100
15 ≤ F ≤ 55	50

If you have any other requests,NDK will study it.

to the Future

NX5032GA

For Automotive

Features

A small surface-mount type crystal unit, ideal for Automotive.

Compatible with an engine control CPU clock delivering the high reliability that is particularly demanded, and compatible with low frequencies starting from 8 MHz.

- •Compact and thin. (5.0 × 3.2 × 1.3 mm typ.)
- •Stable start-up characteristic even under extremely severe environmental conditions.
- •Excellent environmental characteristics, including heat, vibration and shock resistance.
- •Meets the requirements for re-flow profiling using lead-free solder.
- Conforms to AEC-Q200.



Specifications

Item Model	NX5032GA			
Standard	Star	Idard	Optional	
Nominal Frequency (MHz)	8 ≤ F < 10.5	10.5 ≤ F ≤ 40	8 ≤ F ≤ 40	
Overtone Order	Funda	mental	Fundamental	
Frequency Tolerance (25 ±3 °C)	±50 ×	× 10 ⁻⁶	±50 × 10 ⁻⁶	
Frequency versus Temperature Characteristics (with reference to +25 °C)	±150 × 10 ⁻⁶		±150 × 10⁻6	
Operating Temperature Range (°C)	-40 to +150		-40 to +150	
Storage Temperature Range (°C)	-40 to +150		-40 to +150	
Equivalent Series Resistance	Refe	r to *1	Refer to *1	
Level of Drive (µW)	10 (Max. 500)		10 (Max. 500)	
Load Capacitance (pF)	8		6 to 32	
Frequency Aging (+25 °C)			Max. ±10 × 10 ⁻⁶ / year *2	
Specifications Number	STD-CSU-1	Refer to *3		

Please specify the model name, frequency, and specification number when you order products.

For further questions regarding specifications, please feel free to contact us.

*2 If you have any other requests, NDK will study it.

- *3 Ordering information: Overtone Order Fundamental / 3rd Overtone, the Operating Temperature Range, Frequency versus Temperature Characteristics, Frequency Tolerance, and Load Capacitance.
 - Ex. Model, Frequency (24.000000MHz 6digits), S1: Fundamental or S3 : 3rd overtone
 - Operating Temperature Range (-40 to +150°C) Frequency versus Temperature Characteristics (±150 × 10-6)
 - Frequency Tolerance (±50 × 10⁻⁶) Load Capacitance (10pF)
 - NX5032GA
 - 24.000000MHz

S1-40150-150-50-10





*1 Equivalent Series Resistance	ce
---------------------------------	----

Nominal Frequency (MHz)	Equivalent Series Resistance Max. (Ω)		
8 ≤ F < 9.5	300		
9.5 ≤ F < 10	220		
10 ≤ F < 15	150		
15 ≤ F < 20	120		
20 ≤ F < 24	100		
24 ≤ F < 30	80		
30 ≤ F ≤ 40	50		

If you have any other requests, NDK will study it.

Features

A small surface-mount type crystal unit, ideal for the special requirements of automotive, such as TPMS (Tire Pressure Monitoring System). The crystal unit is ideally suited for the clock signal generating source of the transmission unit in a tire wheel that is subject to strong centrifugal force.

- Stable frequency characteristics even with a powerful centrifugal force of 2,000 G, as found in the transmission side of TPMS applications.
- •Excellent environmental performance including heat, vibration, shock and heat cycle resistance.
- •Lead-free. Meets the requirements for re-flow profiling using lead-free solder.
- •Conforms to AEC-Q200.



Pb Free RoHS Compliant Directive 2011/65/EU Directive (EU) 2015/863

Specifications

Item Model	NX5032SD			
Standard	Standard	Optional		
Nominal Frequency (MHz)	9.75 ≤ F ≤ 40	9.75 ≤ F ≤ 40		
Overtone Order	Fundamental	Fundamental		
Frequency Tolerance (25 ±3 °C)	±15 × 10 ⁻⁶	±15 × 10 ⁻⁶		
Frequency versus Temperature Characteristics (with reference to +25 $^{\circ}$ C)	±50 × 10⁻6	±50 × 10⁻⁵		
Operating Temperature Range (°C)	-40 to +125	-40 to +125		
Storage Temperature Range (°C)	-40 to +125	-40 to +125		
Equivalent Series Resistance	Refer to *1	Refer to *1		
Level of Drive (µW)	10 (Max. 100)	10 (Max. 100)		
Load Capacitance (pF)	12	6 to 32		
Ferquency Aging (+25 °C)		Max. ±3 × 10⁻⁶ / year *2		
Specifications Number	STD-CSY-1	Refer to *3		

Please specify the model name, frequency, and specification number when you order products.

For further questions regarding specifications, please feel free to contact us.

*2 If you have any other requests, NDK will study it.

*3 Ordering information: Overtone Order Fundamental / 3rd Overtone, the Operating Temperature Range, Frequency versus Temperature Characteristics, Frequency Tolerance, and Load Capacitance.

Ex. Model, Frequency(24.000000MHz 6digits), S1: Fundamental or S3 : 3rd overtone

- Operating Temperature Range(-40 to +125°C) - Frequency versus Temperature Characteristics (±50 × 10-6)

- Frequency Tolerance $(\pm 15 \times 10^{-6})$ - Load Capacitance (10pF)

NX5032SD

24.000000MHz

S1-40125-50-15-10

■ Dimensions





Land pattern (Recommended)



*1 Equivalent Series Resistance					
Nominal Frequency (MHz)	Equivalent Series Resistance Max. (Ω)				
9.75 ≤ F < 10	150				
10 ≤ F < 15	120				
15 ≤ F < 20	100				
20 ≤ F ≤ 40	80				

If you have any other requests, NDK will study it.

NIHON DEMPA KOGYO CO., LTD.



RoHS Compliant Directive 2011/65/EU Directive (EU) 2015/86

Features

- A small surface-mount type crystal unit.
- Compact and thin. (8.0×4.5×1.8mm)
- Supports low frequencies(from 4MHz).
- · Ideal for OA/AV applications and Accessories for a car.
- Excellent environmental performance, including heat and shock resistance.
- Meets the requirements for re-flow profiling using lead-free solder.



Specifications

Item		NX8045GB					
Standard			Stan	dard			Optional
Nominal Frequency (MHz)	$4 \le F \le 4.9$	$5 \le F \le 7.499$	7.5 ≤ F ≤ 40	$4 \le F \le 4.9$	5 ≤ F ≤ 7.499	7.5 ≤ F ≤ 48	4 ≤ F ≤ 48
Overtone Order			Funda	mental			Fundamental
Frequency Tolerance (25 ±3 °C)		±30 × 10 ⁻⁶			±20 × 10 ⁻⁶		±20 × 10 ⁻⁶
Frequency versus Temperature Characteristics (with reference to +25 °C)		±50 × 10 ⁻⁶		±30 × 10 ⁻⁶			±30 × 10 ⁻⁶
Operating Temperature Range (°C)		-40 to +85		-40 to +85 *2			
Storage Temperature Range (°C)		-40 to +125 -40 to +85					
Equivalent Series Resistance		Refer to *1					
Level of Drive (µW)		50 (Max. 500)					
Load Capacitance (pF)	8						6 to 32
Frequency Aging (+25 °C)						Max. ±10 × 10⁻⁶ / year *2	
Specifications Number	STD-CJL-5	STD-CJL-5 STD-CSF-5 STD-CSF-6 STD-CJL-2 STD-CSF-3 STD-CSF-4					

Please specify the model name, frequency, and specification number when you order products.

For further questions regarding specifications, please feel free to contact us.

*2 If you have any other requests, NDK will study it.

*3 Ordering information: Overtone Order Fundamental / 3rd Overtone, the Operating Temperature Range, Frequency versus Temperature Characteristics, Frequency Tolerance, and Load Capacitance.

Ex. Model, Frequency (24.000000MHz 6digits), S1: Fundamental or S3 : 3rd overtone

- Operating Temperature Range (-40 to +85°C) - Frequency versus Temperature Characteristics (±30 × 10-6)

- Frequency Tolerance (±20 × 10⁻⁶) - Load Capacitance (10pF)

NX8045GB

24.00000MHz

S1-4085-30-20-10

Dimensions



*1 Equivalent Series Resistance

Nominal Frequency (MHz)	Equivalent Series Resistance Max. (Ω)			
4 ≤ F < 5	300			
5 ≤ F < 8	250			
8 ≤ F < 9.5	200 120			
9.5 ≤ F < 10				
10 ≤ F < 12	100			
12 ≤ F < 13	80			
13 ≤ F ≤ 40	50			

If you have any other requests, NDK will study it.

NIHON DEMPA KOGYO CO., LTD.



For OA / AV



Features

- A small surface-mount type crystal unit, ideal for Automotive.
- Supports low frequencies(from 4MHz to 8MHz).
- Small SMD package. (8.0×4.5×2.0mm)
- Excellent environmental characteristics, including heat, vibration and shock resistance.
- High resistance to solder cracking. Excellent performance for wide temperature range heat cycles (-40 to +150°C, 3,000 cycles) when mounted on a glass epoxy circuit board.
- Support a wide operating temperature range(-40 to +150°C).
- Meets the requirements for re-flow profiling using lead-free solder.
- Conforms to AEC-Q200.



RoHS Compliant Directive 2011/65/EU

Specifications

Item Model	NX8045GE				
Standard	Standard Optional				
Nominal Frequency (MHz)	4 ≤ F ≤ 8	$4 \le F \le 8$			
Overtone Order	Fundamental	Fundamental			
Frequency Tolerance (25 ±3 °C)	±50 × 10 ⁻⁶	±50 × 10 ⁻⁶			
Frequency versus Temperature Characteristics (with reference to +25 °C)	±150 × 10⁻6	$\pm 150 \times 10^{-6}$			
Operating Temperature Range (°C)	-40 to +150	-40 to +150			
Storage Temperature Range (°C)	-40 to +150	-40 to +150			
Equivalent Series Resistance (Ω)	Max. 150	Max. 150			
Level of Drive (µW)	50 (Max. 500)	50 (Max. 500)			
Load Capacitance (pF)	8	6 to 32			
Frequency Aging (+25 °C)		Max. ±10 × 10 ⁻⁶ / year *1			
Specifications Number	STD-CJL-6	Refer to *2			

Please specify the model name, frequency, and specification number when you order products.

For further questions regarding specifications, please feel free to contact us.

*1 If you have any other requests, NDK will study it.

*2 Ordering information: Overtone Order Fundamental / 3rd Overtone, the Operating Temperature Range, Frequency versus Temperature Characteristics, Frequency Tolerance, and Load Capacitance.

Ex. Model, Frequency (8.000000MHz 6digits), S1: Fundamental or S3 : 3rd overtone

- Operating Temperature Range (-40 to +150°C) - Frequency versus Temperature Characteristics (±150 × 10-6)

- Frequency Tolerance (±50 × 10⁻⁶) - Load Capacitance (10pF)

NX8045GE

8.000000MHz

S1-40150-150-50-10

Dimensions







Features

A small surface-mount type crystal unit, ideal for Automotive.

Compatible with an engine control CPU clock delivering the high reliability that is particularly demanded.

- Stable start-up characteristic even under extremely severe environmental conditions.
- Excellent environmental characteristics, including heat, vibration and shock resistance.
- Meets the requirements for re-flow profiling using lead-free solder.
- Conforms to AEC-Q200.



RoHS Compliant Directive 2011/65/EU Directive (EU) 2015/863

Specifications

Item Model	NX8045GB				
Standard	Standard	Optional			
Nominal Frequency (MHz)	8 ≤ F ≤ 40	8 ≤ F ≤ 40			
Overtone Order	Fundamental	Fundamental			
Frequency Tolerance (25 ±3 °C)	±50 × 10 ⁻⁶	±50 × 10 ⁻⁶			
Frequency versus Temperature Characteristics (with reference to +25 °C)	±150 × 10 ⁻⁶	$\pm 150 \times 10^{-6}$			
Operating Temperature Range (°C)	-40 to +150	-40 to +150			
Storage Temperature Range (°C)	-40 to +150	-40 to +150			
Equivalent Series Resistance	Refer to *1	Refer to *1			
Level of Drive (µW)	10 (Max. 500)	10 (Max. 500)			
Load Capacitance (pF)	8	6 to 32			
Frequency Aging (+25°C)		Max. ±10 × 10 ⁻⁶ / year *2			
Specifications Number	STD-CSJ-1	Refer to *3			

Please specify the model name, frequency, and specification number when you order products.

For further questions regarding specifications, please feel free to contact us.

*2 If you have any other requests, NDK will study it.

*3 Ordering information: Overtone Order, Fundamental / 3rd Overtone, the Operating Temperature Range, Frequency versus Temperature Characteristics, Frequency Tolerance, and Load Capacitance.

Ex. Model, Frequency (24.000000MHz 6digits), S1: Fundamental or S3 : 3rd overtone

- Operating Temperature Range (-40 to +150°C) - Frequency versus Temperature Characteristics (±150 × 10-6)

- Frequency Tolerance $(\pm 50 \times 10^{-6})$ - Load Capacitance (10pF)

NX8045GB

24.000000MHz

S1-40150-150-50-10

■ Dimensions



*1 Equivalent Series Resistance

Nominal Frequency (MHz)	Equivalent Series Resistance Max. (Ω)
8 ≤ F < 10	220
10 ≤ F ≤ 40	150

If you have any other requests, NDK will study it.



AT-41 / AT-41CD2

Directive 2011/65/EU Directive (EU) 2015/863

For OA / AV

Features

A highly stable and reliable low-height crystal unit with a metallic package, also suitable for surface mounting.

- Compatible with surface mounting.
- Airtight metal package ensures high-reliability.
- Taping package is for customer automatic loading operation.
- AT-41CD2 meets the requirements for re-flow profiling using lead-free solder.

■ Specifications

Item	AT-41			AT-41CD2			AT-41 / AT-41CD2	
Standard			Stan	dard			Optional	
Nominal Frequency (MHz)	3 ≤ F ≤ 37	$3 \le F \le 37$ $26 \le F < 60$ $60 \le F \le 75$			26 ≤ F < 60	60 ≤ F ≤ 75	$4 \le F \le 37$	26 ≤ F ≤ 40
Overtone Order	Fundamental	3rd ov	ertone	Fundamental 3rd overtone			Fundamental	3rd overtone
Frequency Tolerance (25 ±3 °C)		±20 × 10 ⁻⁶			±20 × 10 ⁻⁶		±20 ×	: 10 ⁻⁶
Frequency versus Temperature Characteristics (with reference to +25 °C)	±30 × 10 ⁻⁶			±30 × 10 ⁻⁶			±30 × 10 ⁻⁶	
Operating Temperature Range (°C)		-10 to +70		-10 to +70			-40 to	o +85
Storage Temperature Range (°C)		-40 to +85		-40 to +85		-40 to +85		
Equivalent Series Resistance		Refer to *1		Refer to *1		Refer to *1		
Level of Drive (µW)	Refe	Refer to *2 (Max. 1000)		Refer to *2 (Max. 1000)		1000)	Refer to *2	
Load Capacitance (pF)	16 Series resonance			16 Series resonance		esonance	6 to 32	
Frequency Aging (+25 °C)							Max. ±5 × 1	0 ^{-6/} year *3
Specifications Number	STD-LPH-9 STD-LPH-10 STD-LPH-11			LN-L-0002 STD-LPH-3 STD-LPH-5		-5 Refer to *4		

*1 Equivalent Series Resistance

Overtone

Order

Fundamental

3rd overtone

Nominal

Frequency

(MHz)

3 ≤ F < 3.2 3.2 ≤ F < 3.5

 $3.5 \le F < 4$

 $4 \le F < 4.5$

4.5 ≤ F < 5

5 ≤ F < 6

6 ≤ F < 8

8 ≤ F < 10

10 ≤ F < 12

12 ≤ F ≤ 37

26 ≤ F < 35

35 ≤ F < 48

 $48 \le F \le 75$

ES

40

20

150

120

100

80

70

60

50

40

140

100

80

Max.

*2 Level of Drive

R (Ω)	Overtone Order	Nominal Frequency (MHz)	Level of Drive (µW)		Overtone Order	Nominal Frequency (MHz)	Level of Drive (µW)	
0	Fundamental	3 ≤ F < 5	500		3rd	$26 \le F \le 60$	500	
0	Fundamentar	5 ≤ F ≤ 37	50		overtone	60 ≤ F ≤ 75	10	

Please specify the model name, frequency, and specification number when you order products.

For further questions regarding specifications, please feel free to contact us.

*3 If you have any other requests, NDK will study it.

*4 Ordering information: Overtone Order Fundamental / 3rd Overtone, the Operating Temperature Range, Frequency versus Temperature Characteristics, Frequency Tolerance, and Load Capacitance.

Ex. Model, Frequency (24.000000MHz 6digits), S1: Fundamental or S3 : 3rd overtone – Operating Temperature Range (-40 to +85°C) – Frequency versus Temperature Characteristics (±30 × 10⁻⁶)– Frequency Tolerance (±20 × 10⁻⁶) – Load Capacitance (10pF) AT-41

24.000000MHz

S1-4085-30-20-10

AT-41CD2 10.21max mm 12.7 ± 0.6 Land pattern (Recommended) 11.4 ± 0.3 10.4mm mm 11.4 ± 0.3 10.4mm mm 11.4 ± 0.3 10.4mm mm 11.4 ± 0.3 10.4mm mm 10.21max mm 12.7 ± 0.6 10.4mm mm 10.21max mm 12.7 ± 0.6 10.4mm mm 10.21max mm 10.21max mm 12.7 ± 0.6 10.4mm mm 10.4mm mm

Dimensions



NIHON DEMPA KOGYO CO., LTD.



AT-41CD2



AT-41

Crystal Bridge to the Future



NR-2C / NR-2B

For High Precision Industry

Features

A highly reliable crystal unit with outstanding frequency stability and covering a broad frequency range.

• The product satisfies strict temperature characteristics standards, is shock resistant and has excellent frequency reproducibility.







Specifications

Item Model	NR-2C				NR-2C / NR-2B			
Standard		Standard		Standard				Optional
Nominal Frequency (MHz)	10 ≤ F ≤ 25	45 ≤ F ≤ 95	80 ≤ F ≤150	10 ≤ F ≤ 30	25 ≤ F < 30	30 ≤ F ≤ 75	50 ≤ F ≤100	NR-2C: 10 ≤ F ≤150 NR-2B: 10 ≤ F ≤100
Overtone Order	Fundamental	3rd overtone	5th overtone	Fundamental	3rd overtone	3rd overtone	5th overtone	Fundamental/ 3rd overtone/ 5th overtone
Frequency Tolerance (25 ±3 °C)		±10 × 10⁻6		±10 × 10 ⁻⁶				±10 × 10 ⁻⁶
Frequency versus Temperature Characteristics (with reference to +25 °C)	±5 × 10 ⁻⁶ ±5 × 10 ⁻⁶					±5 × 10 ⁻⁶		
Operating Temperature Range (°C)	-10 to +60 -10 to +60				o +60		-10 to +60	
Storage Temperature Range (°C)		-40 to +85		-40 to +85				-40 to +85
Equivalent Series Resistance (Ω)	Max. 40	Max. 60	Max. 80	Max. 25	Max. 50	Max. 45	Max. 60	
Level of Drive (µW)		10 (Max. 100) 10 (Max. 100)			10 (Max. 100)			
Load Capacitance (pF)	12	Series re	esonance	12 Series resonance			Series or 8 to 20	
Frequency Aging (+25°C)							Max. ±5 × 10⁻⁶ / year *1	
Specifications Number	STD-CMB-4	STD-CMB-5	STD-CMB-6	STD-CMB-1	STD-0	CMB-2	STD-CMB-3	Refer to *2

Please specify the model name, frequency, and specification number when you order products.

For further questions regarding specifications, please feel free to contact us.

*1 If you have any other requests, NDK will study it.

*2 Ordering information: Overtone Order Fundamental / 3rd Overtone, the Operating Temperature Range, Frequency versus Temperature Characteristics, Frequency Tolerance, and Load Capacitance. Ex. Model, Frequency (100.000000MHz 6digits), S1: Fundamental or S3 : 3rd overtone or S5 : 5th overtone – Operating Temperature

Ex. Model, Frequency (100.000000MHz 6digits), S1: Fundamental or S3 : 3rd overtone or S5 : 5th overtone – Operating Temperature Range (−10 to +60°C) – Frequency versus Temperature Characteristics (±5 × 10⁻⁶) – Frequency Tolerance (±10 × 10⁻⁶) – Load Capacitance (8pF)

NR-2C

100.00000MHz

S5-1060-5-10-8

■ Dimensions



NIHON DEMPA KOGYO CO., LTD.



RC-8 / NC-18C

For High Precision Industry

Features

A highly reliable crystal unit with outstanding frequency stability and covering a broad frequency range.

• The product satisfies strict temperature characteristics standards, is shock resistant and has excellent frequency reproducibility.





RoHS Compliant Directive 2011/65/EU Directive (EU) 2015/863

Specifications

Item Model	RC-8	NC-18C	RC-8 / NC-18C
Standard	Standard	Standard	Optional
Nominal Frequency (MHz)	5 ≤ F ≤ 20	10 ≤ F ≤ 20	RC-8 : 5 ≤ F ≤ 20 NC-18C : 10 ≤ F ≤ 20
Overtone Order	3rd overtone	3rd overtone	3rd overtone
Operating Temperature Range (°C)	-40 to +120	-40 to +120	-40 to +120
Storage Temperature Range (°C)	-55 to +125	–55 to +125	-55 to +125
Turnover point (°C)	+70 to +110	+70 to +110	+70 to +110
Frequency Tolerance (at middle of turnover point)	Max. ±3 × 10⁻ੰ	Max. ±3 × 10⁻⁰	Max. ±3 × 10 ⁻⁶
Equivalent Series Resistance (Ω)	Max. 150	Max. 150	Max. 150
Level of Drive (µW)	Max. 100	Max. 100	Max. 100
Load Capacitance (pF)	Series to 32	Series to 32	Series to 32
Frequency Aging (at Turnover point)			Max. ±100 × 10⁻º / year *1 (24H after ref)
Specifications Number	STD-CWB-2	STD-CWB-1	Refer to *2

Please specify the model name, frequency, and specification number when you order products.

For further questions regarding specifications, please feel free to contact us.

*1 If you have any other requests, NDK will study it.

*2 Ordering information: Overtone Order 3rd Overtone, the Operating Temperature Range, Frequency Tolerance, and Load Capacitance. Ex. Model, Frequency(12.000000MHz 6digits), S3 : 3rd overtone – Operating Temperature Range(-40 to +120°C) – Frequency Tolerance(±3 × 10⁻⁶) – Load Capacitance(10pF)

RC-8 12.000000MHz

S3-40120-3-10

