

# 4A/2A Dual Channel Synchronous Step-Down Switcher with Integrated FET

Check for Samples: TPS54495

#### FEATURES

- D-CAP2<sup>™</sup> Control Mode
  - Fast Transient Response
  - No External Parts Required For Loop Compensation
  - Compatible with Ceramic Output Capacitors
- Wide Input Voltage Range : 4.5 V to 18 V
- Output Voltage Range : 0.76 V to 7 V
- Highly Efficient Integrated FETs Optimized for Low Duty Cycle Applications
  - 90 m $\Omega$  (High Side) and 60 m $\Omega$  (Low Side)
- High Initial Reference Accuracy
- Supports Constant 4 A CH1 and 2 A CH2 Load Current
- Low-Side r<sub>DS(on)</sub> Loss-Less Current Sensing
- Adjustable Soft Start
- Non-Sinking Pre-Biased Soft Start
- 700 kHz Switching Frequency
- Cycle-by-Cycle Over-Current Limit Control
- OCL/UVLO/TSD Protections
- Hiccup Timer for Overload Protection
- Adaptive Gate Drivers with Integrated Boost
   PMOS Switch
- OCP Constant Due To Thermally Compensated r<sub>DS(on)</sub> with 4000ppm/°C
- 16-Pin HTSSOP, 16-Pin VQFN
- Auto-Skip Eco-mode™ for High Efficiency at Light Load


#### APPLICATIONS

- Point-of-Load Regulation in Low Power Systems for Wide Range of Applications
  - Digital TV Power Supply
  - Networking Home Terminal
  - Digital Set Top Box (STB)
  - DVD Player/Recorder
  - Gaming Consoles and Other

#### DESCRIPTION

The TPS54495 is a dual, adaptive on-time D-CAP2™ mode synchronous buck converter. The TPS54495 enables system designers to complete the suite of various end equipment's power bus regulators with a cost effective, low component count, and low standby current solution. The main control loops of the TPS54495 use the D-CAP2™ mode control which provides a very fast transient response with no external compensation components. The adaptive ontime control supports seamless transition between PWM mode at higher load conditions and Ecomode<sup>™</sup> operation at light loads. Eco-mode<sup>™</sup> allows the TPS54495 to maintain high efficiency during lighter load conditions. The TPS54495 is able to adapt to both low equivalent series resistance (ESR) output capacitors such as POSCAP or SP-CAP, and ultra-low ESR, ceramic capacitors. The device provides convenient and efficient operation with input voltages from 4.5V to 18V.

The TPS54495 is available in a 4.4 mm  $\times$  5 mm 16pin TSSOP (PWP) package and 4 mm x 4 mm 16-pin VQFN (RSA), and is designed to operate for an ambient temperature range from -40°C to 85°C.



Please be aware that an important notice concerning availability, standard warranty, and use in critical applications of Texas Instruments semiconductor products and disclaimers thereto appears at the end of this data sheet. D-CAP2, Eco-mode, Eco-Mode are trademarks of Texas Instruments.

## TPS54495



www.ti.com

#### SLVSBH0A-JUNE 2012-REVISED MAY 2013



These devices have limited built-in ESD protection. The leads should be shorted together or the device placed in conductive foam during storage or handling to prevent electrostatic damage to the MOS gates.

T <sub>A</sub>	PACKAGE <sup>(2)</sup> (3)	ORDERING PART NUMBER	PINS	OUTPUT SUPPLY					
	PWP	TPS54495PWPR	16	Tape-and-Reel					
40°C to 95°C	PVVP	TPS54495PWP	16	Tube					
–40°C to 85°C −		TPS54495RSAR	16	Tone and Deal					
	RSA	TPS54495RSAT	16	Tape-and-Reel					

#### **ORDERING INFORMATION**<sup>(1)</sup>

For the most current package and ordering information, see the Package Option Addendum at the end of this document, or see the TI web site at www.ti.com

(2) Package drawings, thermal data, and symbolization are available at www.ti.com/packaging.

(3) All packaging options have Cu NIPDAU lead/ball finish.

#### ABSOLUTE MAXIMUM RATINGS

over operating free-air temperature range (unless otherwise noted)<sup>(1) (2)</sup>

			VALUE	UNIT
		VIN1, VIN2, EN1, EN2	-0.3 to 20	
		VBST1, VBST2	-0.3 to 26	
		VBST1, VBST2 (10ns transient)	-0.3 to 28	
	Input voltage range	VBST1-SW1, VBST2-SW2	-0.3 to 6.5	V
		VFB1, VFB2	-0.3 to 6.5	
		SW1, SW2	-2 to 20	
		SW1, SW2 (10ns transient)	-3 to 22	
		VREG5, SS1, SS2	-0.3 to 6.5	
	Output voltage range	PGND1, PGND2	-0.3 to 0.3	V
	Electrestatio discharge	Human Body Model (HBM)	2	kV
	Electrostatic discharge	Charged Device Model (CDM)	500	V
T <sub>A</sub>	Operating ambient tempe	erature range	-40 to 85	°C
T <sub>STG</sub>	Storage temperature ran	-55 to 150	°C	
TJ	Junction temperature rar	ge	-40 to 150	°C

(1) Stresses beyond those listed under "absolute maximum ratings" may cause permanent damage to the device. These are stress ratings only and functional operation of the device at these or any other conditions beyond those indicated under "recommended operating conditions" are not implied. Exposure to absolute-maximum-rated conditions for extended periods may affect device reliability.

(2) All voltages are with respect to IC GND terminal.

#### THERMAL INFORMATION

	THERMAL METRIC <sup>(1)</sup>	TPS	TPS54495				
		PWP (16) PINS	RSA (16) PINS	UNITS			
$\theta_{JA}$	Junction-to-ambient thermal resistance	41.4	32.8				
$\theta_{JCtop}$	Junction-to-case (top) thermal resistance	27.8	35.4				
$\theta_{JB}$	Junction-to-board thermal resistance	23.2	9.9	°C/W			
$\Psi_{JT}$	Junction-to-top characterization parameter	0.9	0.4	°C/vv			
$\Psi_{JB}$	Junction-to-board characterization parameter	23.0	10.0				
$\theta_{JCbot}$	Junction-to-case (bottom) thermal resistance	3.5	1.6				

(1) For more information about traditional and new thermal metrics, see the IC Package Thermal Metrics application report, SPRA953.



SLVSBH0A -JUNE 2012-REVISED MAY 2013

www.ti.com

#### **RECOMMENDED OPERATING CONDITIONS**

over operating free-air temperature range (unless otherwise noted)

			VAL	MIN         MAX           4.5         18           -0.1         24           -0.1         27           -0.1         5.7		
			MIN	MAX	UNIT	
	Supply input voltage range	VIN1, VIN2	4.5	18	V	
		VBST1, VBST2	-0.1	24		
		VBST1, VBST2 (10ns transient)	-0.1	27		
	Input voltage range	VBST1-SW1, VBST2-SW2	-0.1	5.7		
		VFB1, VFB2	-0.1	5.7	V	
		EN1, EN2	-0.1	18		
		SW1, SW2	-1.0	18		
		SW1, SW2 (10ns transient)	-3	21		
		VREG5, SS1, SS2	-0.1	5.7		
	Output voltage range	PGND1, PGND2	-0.1	0.1	V	
		VO1, VO2	0.76	7.0		
T <sub>A</sub>	Operating free-air temperatur	e	-40	85	°C	
TJ	Operating Junction Temperation	ture	-40	150	°C	

#### ELECTRICAL CHARACTERISTICS<sup>(1)</sup>

over recommended free-air temperature range, VIN = 12 V (unless otherwise noted)

	PARAMETER	CONDITIONS	MIN	TYP	MAX	UNIT
SUPPLY C	URRENT	I				
I <sub>IN</sub>	VIN supply current	VIN supply current $T_A = 25^{\circ}C$ , EN1 = EN2 = 5 V, VFB1 = VFB2 = 0.8 V				
I <sub>VINSDN</sub>	VIN shutdown current	$T_A = 25^{\circ}C$ , EN1 = EN2 = L after H		15	20	μA
FEEDBAC	K VOLTAGE					
V <sub>VFBTHLx</sub>	VFBx threshold voltage	T <sub>A</sub> = 25°C, CH1 = 3.3 V, CH2 = 1.5 V	758	765	773	mV
TC <sub>VFBx</sub>	Temperature coefficient	On the basis of 25°C <sup>(2)</sup>	-115		115	ppm/°C
I <sub>VFBx</sub>	VFBx Input Current	VFBx = 0.8 V, T <sub>A</sub> = 25°C	-0.4	0.2	0.4	μA
VREG5 OU	ТРИТ					
V <sub>VREG5</sub>	VREG5 output voltage	$T_{A} = 25^{\circ}C, 6 \text{ V} < \text{VIN1} < 18 \text{ V},$ $I_{\text{VREG}} = 5 \text{ mA}$		5.5		V
I <sub>VREG5</sub>	Output current	VIN1 = 6 V, VREG5 = 4.0 V, $T_A = 25^{\circ}C^{(2)}$		75		mA
MOSFETs		I				
r <sub>DS(on)H</sub>	High side switch resistance	$T_A = 25^{\circ}C$ , VBSTx-SWx = 5.5 V <sup>(2)</sup>		90		mΩ
r <sub>DS(on)L</sub>	Low side switch resistance	$T_{A} = 25^{\circ}C^{(2)}$		60		mΩ
ON-TIME T	IMER CONTROL	•			*	
T <sub>ON1</sub>	SW1 On Time	SW1 = 12 V, VO1 = 1.2 V		165		ns
T <sub>ON2</sub>	SW2 On Time	SW2 = 12 V, VO2 = 1.2 V		165		ns
T <sub>OFF1</sub>	SW1 Min off time	$T_A = 25^{\circ}C$ , VFB1 = 0.7 V <sup>(2)</sup>		220		ns
T <sub>OFF2</sub>	SW2 Min off time	$T_A = 25^{\circ}C$ , VFB2 = 0.7 V <sup>(2)</sup>		220		ns
SOFT STAI	RT	•	-+			
I <sub>SSC</sub>	SSx charge current	VSSx = 0.5 V, T <sub>A</sub> = 25°C	-8.4	-8.0	-7.6	μA
TC <sub>ISSC</sub>	I <sub>SSC</sub> temperature coefficient	On the basis of 25°C <sup>(2)</sup>	-5		4	nA/°C
I <sub>SSD</sub>	SSx discharge current	VSSx = 0.5 V	3	7	10	mA

(1) x means either 1 or 2, that is VFBx means VFB1 or VFB2.

(2) Specified by design. Not production tested.

EXAS NSTRUMENTS

#### ELECTRICAL CHARACTERISTICS<sup>(1)</sup> (continued)

over recommended free-air temperature range, VIN = 12 V (unless otherwise noted)

	PARAMETER	CONDITIONS	MIN	TYP	MAX	UNIT
UVLO		L				
V	VREG5 UVLO threshold	VREG5 rising		3.83		V
V <sub>UVREG5</sub> VREG5 UVLO threshold		Hysteresis		0.6		v
LOGIC THE	ESHOLDs					
V <sub>ENxH</sub>	ENx H-level threshold voltage		2.0			V
V <sub>ENxL</sub>	ENx L-level threshold voltage				0.4	V
R <sub>ENx_IN</sub>	ENx input resistance	ENx = 12V	225	450	900	kΩ
CURRENT	LIMITs					
I <sub>OCL1</sub>	CH1 Current limit	$L_{OUT1} = 2.2 \ \mu H^{(3)}$	4.5	5.7	7.0	А
I <sub>OCL2</sub>	CH1 Current limit	L <sub>OUT2</sub> = 1.5 μH <sup>(3)</sup>	2.8	3.9	5.0	А
OUTPUT U	NDERVOLTAGE AND OVERVOLTAGE	E PROTECTION (UVP, OVP)				
V <sub>UVP</sub>	Output UVP trip threshold	measured on VFBx	63%	68%	73%	
T <sub>UVPDEL</sub>	Output UVP delay time			1.5		ms
T <sub>UVPEN</sub>	Output UVP enable delay	UVP enable delay / softstart time	x 1.4	x 1.7	x 2.0	
	SHUTDOWN					
		Shutdown temperature <sup>(3)</sup>		155		°C
T <sub>SD</sub>	Thermal shutdown threshold	Hysteresis <sup>(3)</sup>	25		Ĵ	


(3) Specified by design. Not production tested.

4 Submit Documentation Feedback



SLVSBH0A -JUNE 2012-REVISED MAY 2013

#### **DEVICE INFORMATION**




#### PIN FUNCTIONS<sup>(1)</sup>

	PIN		1/0	DESCRIPTION
NAME	PWP	RSA	I/O	DESCRIPTION
VIN1	1	3	Ι	Power inputs and connects to both high side NFET drains.
VIN2	16	2	Ι	Supply Input for 5.5 V linear regulator.
VBST1	2	4	Ι	Supply input for high-side NFET gate drive circuit. Connect 0.1 µF ceramic
VBST2	15	1	Ι	capacitor between VBSTx and SWx pins. An internal diode is connected between VREG5 and VBSTx
SW1	3	5	I/O	Switch node connections for both the high-side NFETs and low-side NFETs.
SW2	14	16	I/O	Input of current comparator.
PGND1	4	6	I/O	
PGND2	13	15	I/O	Ground returns for low-side MOSFETs. Input of current comparator.
EN1	5	7	Ι	Enable Dull Lick to enable according converter
EN2	12	14	Ι	Enable. Pull High to enable according converter.
SS1	6	8	0	Soft-Start Programming Pin. Connect Capacitor from SSx pin to GND to
SS2	11	13	0	program Soft-Start time.
VFB1	7	9	Ι	D CAP2 feedback inpute Connect to output valeage with register divider
VFB2	10	12	Ι	<ul> <li>D-CAP2 feedback inputs. Connect to output voltage with resistor divider.</li> </ul>
GND	8	10	I/O	Signal GND. Connect sensitive SSx and VFBx returns to GND at a single point.
VREG5	9	11	0	Output of 5.5 V linear regulator. Bypass to GND with a high-quality ceramic capacitor of at least 1 $\mu$ F. VREG5 is active when VIN1 is added.
Exposed Thermal Pad	Back side	Back side	I/O	Thermal pad of the package. Must be soldered to achieve appropriate dissipation. Must be connected to GND.

(1) x means either 1 or 2, that is. VFBx means VFB1 or VFB2.

Texas Instruments

#### FUNCTIONAL BLOCK DIAGRAM



6



#### **OVERVIEW**

The TPS54495 is a 4A/2A dual synchronous step-down (buck) converter with two integrated N-channel MOSFETs for each channel. It operates using D-CAP2<sup>™</sup> control mode. The fast transient response of D-CAP2<sup>™</sup> control reduces the required output capacitance to meet a specific level of performance. Proprietary internal circuitry allows the use of low ESR output capacitors including ceramic and special polymer types.

#### **DETAILED DESCRIPTION**

#### **PWM Operation**

The main control loop of the TPS54495 is an adaptive on-time pulse width modulation (PWM) controller that supports a proprietary D-CAP2<sup>™</sup> control mode. D-CAP2<sup>™</sup> control combines constant on-time control with an internal compensation circuit for pseudo-fixed frequency and low external component count configuration with both low ESR and ceramic output capacitors. It is stable even with virtually no ripple at the output.

At the beginning of each cycle, the high-side MOSFET is turned on. This MOSFET is turned off when the internal timer expires. This timer is set by the converter's input voltage, VINx, and the output voltage, VOx, to maintain a pseudo-fixed frequency over the input voltage range hence it is called adaptive on-time control. The timer is reset and the high-side MOSFET is turned on again when the feedback voltage falls below the nominal output voltage. An internal ramp is added to the reference voltage to simulate output voltage ripple, eliminating the need for ESR induced output ripple from D-CAP<sup>™</sup> control.

#### **PWM Frequency and Adaptive On-Time Control**

TPS54495 uses an adaptive on-time control scheme and does not have a dedicated on board oscillator. The TPS54495 runs with a pseudo-fixed frequency of 700 kHz by using the input voltage and output voltage to set the on-time timer. The on-time is inversely proportional to the input voltage and proportional to the output voltage, therefore, when the duty ratio is VOx/VINx, the frequency is constant.

#### Auto-Skip Eco-Mode™ Control

The TPS54495 is designed with Auto-Skip Eco-mode<sup>TM</sup> to increase light load efficiency. As the output current decreases from heavy load condition, the inductor current also reduces and eventually comes to the point where its ripple valley touches the zero level, which is the boundary between continuous conduction and discontinuous conduction modes. The rectifying MOSFET is turned off when zero inductor current is detected. As the load current further decreases the converter runs into discontinuous conduction mode. The on-time is kept almost the same as it was in the continuous conduction mode because it takes longer to discharge the output capacitor with smaller load current to the nominal output voltage. The transition point to the light load operation  $I_{Ox(LL)}$  current can be estimated with Equation 1 with 700-kHz used as  $f_{SW}$ .

$$I_{Ox(LL)} = \frac{1}{2 \times L1x \times f_{SW}} \times \frac{(V_{INx} - V_{Ox}) \times V_{Ox}}{V_{INx}}$$
(1)

#### Soft Start and Pre-Biased Soft Start

The soft start time is adjustable. When the ENx pin becomes high,  $8-\mu$ A current begins charging the capacitor which is connected from the SSx pin to GND. Smooth control of the output voltage is maintained during start up. The equation for the slow start time is shown in Equation 2. VFBx voltage is 0.765-V and SSx pin source current is  $8-\mu$ A.

$$T_{SS}(ms) = \frac{C4x(nF) \times VFBx(V)}{I_{SS}(\mu A)} = \frac{C4x(nF) \times 0.765 V}{8 \mu A}$$
(2)

The TPS54495 contains a unique circuit to prevent current from being pulled from the output during startup if the output is pre-biased. When the soft-start commands a voltage higher than the pre-bias level (internal soft start becomes greater than internal feedback voltage VFBx), the controller slowly activates synchronous rectification by starting the first low side FET gate driver pulses with a narrow on-time. It then increments that on-time on a cycle-by-cycle basis until it coincides with the time dictated by (1-D), where D is the duty cycle of the converter. This scheme prevents the initial sinking of the pre-biased output, and ensures that the output voltage (VOx) starts and ramps up smoothly into regulation from pre-biased startup to normal mode operation.

Copyright © 2012–2013, Texas Instruments Incorporated



#### **Current Sensing and Over-Current Protection**

The output over-current protection (OCP) is implemented using a cycle-by-cycle valley detection control circuit. The switch current is monitored by measuring the low-side FET switch voltage between the SWx and PGNDx pins. This voltage is proportional to the switch current and the on-resistance of the FET. To improve the measurement accuracy, the voltage sensing is temperature compensated.

During the on-time of the high-side FET switch, the switch current increases at a linear rate determined by VINx, VOx, the on-time and the output inductor value. During the on-time of the low-side FET switch, this current decreases linearly. The average value of the switch current is the load current  $I_{Ox}$ . If the sensed voltage on the low-side FET is above the voltage proportional to the current limit, the converter keeps the low-side switch on until the measured voltage falls below the voltage corresponding to the current limit and a new switching cycle begins. In subsequent switching cycles, the on-time is set to the value determined for CCM and the current is monitored in the same manner.

Important considerations for this type of over-current protection: The load current is one half of the peak-to-peak inductor current higher than the over-current threshold. Also when the current is being limited, the output voltage tends to fall as the demanded load current may be higher than the current available from the converter. When the over current condition is removed, the output voltage returns to the regulated value. This protection is non-latching.

#### Undervoltage Protection and Hiccup Mode

Hiccup mode of operation protects the power supply from being damaged during an over-current fault condition. If the OCL comparator circuit detects an over-current event the output voltage falls. When the feedback voltage falls below 68% of the reference voltage, the UVP comparator output goes high and an internal UVP delay counter begins counting. After counting UVP delay time, the TPS54495 shuts off the power supply for a given time (7x UVP Enable Delay Time) and then tries to re-start the power supply. If the over-load condition has been removed, the power supply starts and operates normally; otherwise, the TPS54495 detects another over-current event and shuts off the power supply again, repeating the previous cycle. Excess heat due to overload lasts for only a short duration in the hiccup cycle, therefore the junction temperature of the power device is much lower.

#### **UVLO Protection**

Under-voltage lock out protection (UVLO) monitors the voltage of the  $V_{REG5}$  pin. When the  $V_{REG5}$  voltage is lower than the UVLO threshold, the TPS54495 shuts down. As soon as the voltage increases above the UVLO threshold, the converter starts again.


#### Thermal Shutdown

TPS54495 monitors its temperature. If the temperature exceeds the threshold value (typically 155°C), the device shuts down. When the temperature falls below the threshold, the IC starts again.

When VIN1 starts up and VREG5 output voltage is below its nominal value, the thermal shutdown threshold is lower than 155°C. As long as VIN1 rises, T<sub>J</sub> must be kept below 110°C.



SLVSBH0A -JUNE 2012-REVISED MAY 2013



**TYPICAL CHARACTERISTICS** 



Figure 6. VO1=3.3V Output Voltage vs Input Voltage

1.55

1.54 1.53

1.52

1.48 1.47

1.46

1.45

3+


Ch1 Ch3

(2).1

Output Voltage (V) 1.51 1.50 1.49 ÈXAS ISTRUMENTS

www.ti.com

SLVSBH0A-JUNE 2012-REVISED MAY 2013



One output is enabled unless otherwise noted.  $V_{IN} = VIN1$  or VIN2.  $V_{INx} = 12$  V,  $T_A = 25^{\circ}C$  (unless otherwise noted).

G012





SLVSBH0A-JUNE 2012-REVISED MAY 2013

#### **TYPICAL CHARACTERISTICS (continued)**

One output is enabled unless otherwise noted. V<sub>IN</sub> = VIN1 or VIN2. V<sub>INx</sub> = 12 V, T<sub>A</sub> = 25°C (unless otherwise noted).





Figure 18. VO1=3.3V, SW-frequency vs Output Current

EXAS STRUMENTS

SLVSBH0A-JUNE 2012-REVISED MAY 2013





#### SLVSBH0A - JUNE 2012-REVISED MAY 2013

#### DESIGN GUIDE

#### Step By Step Design Procedure

To begin the design process, you must know a few application parameters:

- Input voltage range
- Output voltage
- Output current

In all formulas x is used to indicate that they are valid for both converters. For the calculations the estimated switching frequency of 700 kHz is used.




Figure 24. Schematic Diagram for the Design Example

#### **Output Voltage Resistors Selection**

The output voltage is set with a resistor divider from the output node to the VFBx pin. It is recommended to use 1% tolerance or better divider resistors. Start by using Equation 3 to calculate  $V_{Ox}$ .

To improve the efficiency at very light loads consider using larger value resistors, but too high resistance values will be more susceptible to noise and voltage errors due to the VFBx input current will be more noticeable.

$$V_{Ox} = 0.765 V \times \left(1 + \frac{R1x}{R2x}\right)$$

#### **Output Filter Selection**

The output filter used with the TPS54495 is an LC circuit. This LC filter has double pole at:

$$F_{\rm P} = \frac{1}{2\pi\sqrt{L1x \times C1x}} \tag{4}$$

(3)



#### SLVSBH0A-JUNE 2012-REVISED MAY 2013

At low frequencies, the overall loop gain is set by the output set-point resistor divider network and the internal gain of the TPS545495. The low frequency phase is 180 degrees. At the output filter pole frequency, the gain rolls off at a -40 dB per decade rate and the phase drops rapidly. D-CAP2<sup>TM</sup> introduces a high frequency zero that reduces the gain roll off to -20 dB per decade and increases the phase to 90 degrees one decade above the zero frequency. The inductor and capacitor selected for the output filter must be selected so that the double pole of Equation 4 is located below the high frequency zero but close enough that the phase boost provided by the high frequency zero provides adequate phase margin for a stable circuit. To meet this requirement use the values recommended in Table 1.

Output Voltage (V)	R1x (kΩ)	R2x (kΩ)	Cffx (pF) <sup>(1)</sup>	L1x (µH)	C2x (µF)
1	6.81	22.1		1.5 - 2.2	20 - 68
1.05	8.25	22.1		1.5 - 2.2	20 - 68
1.2	12.7	22.1		1.5 - 2.2	20 - 68
1.5	21.5	22.1		1.5 - 2.2	20 - 68
1.8	30.1	22.1	5 - 22	2.2 - 3.3	20 - 68
2.5	49.9	22.1	5 - 22	2.2 - 3.3	20 - 68
3.3	73.2	22.1	5 - 22	2.2 - 3.3	20 - 68
5	124	22.1	5 - 22	4.7	20 - 68
6.5	165	22.1	5 - 22	4.7	20 - 68

#### **Table 1. Recommended Component Values**

#### (1) Optional

For higher output voltages at or above 1.8 V, additional phase boost can be achieved by adding a feed forward capacitor (Cffx) in parallel with R1x.

The inductor peak-to-peak ripple current, peak current and RMS current are calculated using Equation 5, Equation 6 and Equation 7. The inductor saturation current rating must be greater than the calculated peak current and the RMS or heating current rating must be greater than the calculated RMS current.

For the calculations, use 700 kHz as the switching frequency,  $f_{SW}$ . Make sure the chosen inductor is rated for the peak current of Equation 6 and the RMS current of Equation 7.

$$\Delta I_{L1x} = \frac{V_{Ox}}{V_{INx(MAX)}} \times \frac{V_{INx(MAX)} - V_{Ox}}{L1x \times f_{SW}}$$
(5)

$$I_{L1xpeak} = I_{Ox} + \frac{\Delta I_{L1x}}{2}$$
(6)

$$I_{L1x(RMS)} = \sqrt{I_{Ox}^{2} + \frac{1}{12}\Delta I_{L1x}^{2}}$$
(7)

For the above design example, the calculated peak current is 4.46 A and the calculated RMS current is 4.01 A for VO2. The inductor used is a TDK CLF7045T-2R2N with a rated current of 5.5A based on the inductance change, and of 4.3A based on the temperature rise.

The capacitor value and ESR determines the amount of output voltage ripple. The TPS54495 is intended for use with ceramic or other low ESR capacitors. The recommended value range is from  $20\mu$ F to  $68\mu$ F. Use Equation 8 to determine the required RMS current rating for the output capacitor(s).

$$I_{C2x(RMS)} = \frac{V_{Ox} \times (V_{INx} - V_{Ox})}{\sqrt{12} \times V_{INx} \times L1x \times f_{SW}}$$
(8)

For this design two TDK C3216X5R0J226M 22 $\mu$ F output capacitors are used. The typical ESR is 2 m $\Omega$  each. The calculated RMS current is 0.19A and each output capacitor is rated for 4A.



#### **Input Capacitor Selection**

The TPS54495 requires an input decoupling capacitor and a bulk capacitor is needed depending on the application. A ceramic capacitor of or above  $10\mu$ F is recommended for the decoupling capacitor. Additionally, 0.1  $\mu$ F ceramic capacitors from pin 1 and Pin 16 to ground are recommended to improve the stability and reduce the SWx node overshoots. The capacitors voltage rating needs to be greater than the maximum input voltage.

#### **Bootstrap Capacitor Selection**

A 0.1 µF ceramic capacitors must be connected between the VBSTx and SWx pins for proper operation. It is recommended to use ceramic capacitors with a dielectric of X5R or better.

#### VREG5 Capacitor Selection

A 1  $\mu$ F ceramic capacitor must be connected between the VREG5 and GND pins for proper operation. It is recommended to use a ceramic capacitor with a dielectric of X5R or better.

#### Thermal Information

This 16-pin PWP package incorporates an exposed thermal pad. The thermal pad must be soldered directly to the printed circuit board (PCB). After soldering, the PCB is used as a heatsink. In addition, through the use of thermal vias, the thermal pad can be attached directly to the appropriate copper plane shown in the electrical schematic for the device, or alternatively, can be attached to a special heatsink structure designed into the PCB. This design optimizes the heat transfer from the integrated circuit (IC).

For additional information on the exposed thermal pad and how to use the advantage of its heat dissipating abilities, refer to the Technical Brief, *PowerPAD™ Thermally Enhanced Package*, Texas Instruments Literature No. SLMA002 and Application Brief, *PowerPAD™ Made Easy*, Texas Instruments Literature No. SLMA004.

The exposed thermal pad dimensions for this package are shown in the following illustration.




Figure 25. Thermal Pad Dimensions

#### Layout Considerations


- 1. Keep the input current loop as small as possible. And avoid the input switching current through the thermal pad.
- 2. Keep the SW node as physically small and short as possible to minimize parasitic capacitance and inductance and to minimize radiated emissions.
- 3. Keep analog and non-switching components away from switching components.
- 4. Make a single point connection from the signal ground to power ground.
- 5. Do not allow switching currents to flow under the device.
- 6. Keep the pattern lines for VINx and PGNDx broad.

## **TPS54495**

TEXAS INSTRUMENTS

SLVSBH0A-JUNE 2012-REVISED MAY 2013

- 7. Exposed pad of device must be soldered to PGND.
- 8. VREG5 capacitor should be placed near the device, and connected to GND.
- 9. Output capacitors should be connected with a broad pattern to the PGND.
- 10. Voltage feedback loops should be as short as possible, and preferably with ground shields.
- 11. Kelvin connections should be brought from the output to the feedback pin of the device.
- 12. Providing sufficient vias is preferable for VIN, SW and PGND connections.
- 13. PCB pattern for VIN, SW, and PGND should be as broad as possible.
- 14. VIN Capacitor should be placed as near as possible to the device.



 $\bigcirc$  Via to GND Plane

- Blue parts can be placed on the bottom side
- Connect the SWx pins through another layer with the inductor (yellow line)

Figure 26. TPS54495 PWP Package Layout

Texas

INSTRUMENTS




Figure 27. RSA Package Layout

# **REVISION HISTORY**

# Changes from Original (June 2012) to Revision A Page • Added 16-pin VQFN package to the Features and Description 1 • Added the RSA 16 pin package to the Ordering Information table 2 • Added the RSA package to the Thermal Information table 2 • Added the RSA 16 pin package pinout image, pin names and functions to the DEVICE INFORMATION section 5 • Added Figure 27 17



www.ti.com



#### **PACKAGING INFORMATION**

Orderable Device	Status	Package Type	•	Pins	•	Eco Plan	Lead/Ball Finish	MSL Peak Temp	Op Temp (°C)	Device Marking	Samples
	(1)		Drawing		Qty	(2)		(3)		(4/5)	
TPS54495PWP	ACTIVE	HTSSOP	PWP	16	90	Green (RoHS & no Sb/Br)	CU NIPDAU	Level-2-260C-1 YEAR	-40 to 85	PS54495	Samples
TPS54495PWPR	ACTIVE	HTSSOP	PWP	16	2000	Green (RoHS & no Sb/Br)	CU NIPDAU	Level-2-260C-1 YEAR	-40 to 85	PS54495	Samples
TPS54495RSAR	ACTIVE	QFN	RSA	16	3000	Green (RoHS & no Sb/Br)	CU NIPDAU	Level-2-260C-1 YEAR	-40 to 85	TPS 54495	Samples
TPS54495RSAT	ACTIVE	QFN	RSA	16	250	Green (RoHS & no Sb/Br)	CU NIPDAU	Level-2-260C-1 YEAR	-40 to 85	TPS 54495	Samples

<sup>(1)</sup> The marketing status values are defined as follows:

ACTIVE: Product device recommended for new designs.

LIFEBUY: TI has announced that the device will be discontinued, and a lifetime-buy period is in effect.

NRND: Not recommended for new designs. Device is in production to support existing customers, but TI does not recommend using this part in a new design.

PREVIEW: Device has been announced but is not in production. Samples may or may not be available.

**OBSOLETE:** TI has discontinued the production of the device.

<sup>(2)</sup> Eco Plan - The planned eco-friendly classification: Pb-Free (RoHS), Pb-Free (RoHS Exempt), or Green (RoHS & no Sb/Br) - please check http://www.ti.com/productcontent for the latest availability information and additional product content details.

**TBD:** The Pb-Free/Green conversion plan has not been defined.

**Pb-Free (RoHS):** TI's terms "Lead-Free" or "Pb-Free" mean semiconductor products that are compatible with the current RoHS requirements for all 6 substances, including the requirement that lead not exceed 0.1% by weight in homogeneous materials. Where designed to be soldered at high temperatures, TI Pb-Free products are suitable for use in specified lead-free processes.

**Pb-Free (RoHS Exempt):** This component has a RoHS exemption for either 1) lead-based flip-chip solder bumps used between the die and package, or 2) lead-based die adhesive used between the die and leadframe. The component is otherwise considered Pb-Free (RoHS compatible) as defined above.

Green (RoHS & no Sb/Br): TI defines "Green" to mean Pb-Free (RoHS compatible), and free of Bromine (Br) and Antimony (Sb) based flame retardants (Br or Sb do not exceed 0.1% by weight in homogeneous material)

<sup>(3)</sup> MSL, Peak Temp. -- The Moisture Sensitivity Level rating according to the JEDEC industry standard classifications, and peak solder temperature.

<sup>(4)</sup> There may be additional marking, which relates to the logo, the lot trace code information, or the environmental category on the device.

(5) Multiple Device Markings will be inside parentheses. Only one Device Marking contained in parentheses and separated by a "~" will appear on a device. If a line is indented then it is a continuation of the previous line and the two combined represent the entire Device Marking for that device.

Important Information and Disclaimer: The information provided on this page represents TI's knowledge and belief as of the date that it is provided. TI bases its knowledge and belief on information provided by third parties, and makes no representation or warranty as to the accuracy of such information. Efforts are underway to better integrate information from third parties. TI has taken and



4-Jul-2013

continues to take reasonable steps to provide representative and accurate information but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals. TI and TI suppliers consider certain information to be proprietary, and thus CAS numbers and other limited information may not be available for release.

In no event shall TI's liability arising out of such information exceed the total purchase price of the TI part(s) at issue in this document sold by TI to Customer on an annual basis.

# PACKAGE MATERIALS INFORMATION

www.ti.com

Texas Instruments

#### TAPE AND REEL INFORMATION





## QUADRANT ASSIGNMENTS FOR PIN 1 ORIENTATION IN TAPE



*A	I dimensions are nominal												
	Device	•	Package Drawing		SPQ	Reel Diameter (mm)	Reel Width W1 (mm)	A0 (mm)	B0 (mm)	K0 (mm)	P1 (mm)	W (mm)	Pin1 Quadrant
	TPS54495PWPR	HTSSOP	PWP	16	2000	330.0	12.4	6.9	5.6	1.6	8.0	12.0	Q1
	TPS54495RSAR	QFN	RSA	16	3000	330.0	12.4	4.25	4.25	1.15	8.0	12.0	Q2
	TPS54495RSAT	QFN	RSA	16	250	180.0	12.4	4.25	4.25	1.15	8.0	12.0	Q2

TEXAS INSTRUMENTS

www.ti.com

# PACKAGE MATERIALS INFORMATION


13-Feb-2016



\*All dimensions are nominal

Device	Package Type	Package Drawing	Pins	SPQ	Length (mm)	Width (mm)	Height (mm)
TPS54495PWPR	HTSSOP	PWP	16	2000	367.0	367.0	38.0
TPS54495RSAR	QFN	RSA	16	3000	367.0	367.0	35.0
TPS54495RSAT	QFN	RSA	16	250	210.0	185.0	35.0


# **MECHANICAL DATA**



NOTES: A. All linear dimensions are in millimeters. Dimensioning and tolerancing per ASME Y14.5M-1994.

- B. This drawing is subject to change without notice.
- C. Quad Flatpack, No-leads (QFN) package configuration.
- D. The package thermal pad must be soldered to the board for thermal and mechanical performance.
- E. See the additional figure in the Product Data Sheet for details regarding the exposed thermal pad features and dimensions.
- F. Falls within JEDEC MO-220.






A. All linear dimensions are in millimeters



RSA (S-PVQFN-N16)

PLASTIC QUAD FLATPACK NO-LEAD



NOTES: A. All linear dimensions are in millimeters.

- B. This drawing is subject to change without notice.
- C. Publication IPC-7351 is recommended for alternate designs.
- D. This package is designed to be soldered to a thermal pad on the board. Refer to Application Note, QFN Packages, Texas Instruments Literature No. SLUA271, and also the Product Data Sheets for specific thermal information, via requirements, and recommended board layout. These documents are available at www.ti.com <a href="http://www.ti.com">http://www.ti.com</a>.
- E. Laser cutting apertures with trapezoidal walls and also rounding corners will offer better paste release. Customers should contact their board assembly site for stencil design recommendations. Refer to IPC 7525 for stencil design considerations.
- $\mathsf{F}.$  Customers should contact their board fabrication site for solder mask tolerances.



# **GENERIC PACKAGE VIEW**

# **PWP 16**

# PowerPAD<sup>™</sup> TSSOP - 1.2 mm max height

PLASTIC SMALL OUTLINE



Images above are just a representation of the package family, actual package may vary. Refer to the product data sheet for package details.




# **PACKAGE OUTLINE**

PowerPAD<sup>™</sup> TSSOP - 1.2 mm max height

# **PWP0016J**

#### SMALL OUTLINE PACKAGE



NOTES:

PowerPAD is a trademark of Texas Instruments.

- 1. All linear dimensions are in millimeters. Any dimensions in parenthesis are for reference only. Dimensioning and tolerancing per ASME Y14.5M. 2. This drawing is subject to change without notice. 3. This dimension does not include mold flash, protrusions, or gate burrs. Mold flash, protrusions, or gate burrs shall not

- exceed 0.15 mm per side. 4. Reference JEDEC registration MO-153.




# **PWP0016J**

# **EXAMPLE BOARD LAYOUT**

# PowerPAD<sup>™</sup> TSSOP - 1.2 mm max height

SMALL OUTLINE PACKAGE



NOTES: (continued)

- 5. Publication IPC-7351 may have alternate designs.
- 6. Solder mask tolerances between and around signal pads can vary based on board fabrication site.
- 7. This package is designed to be soldered to a thermal pad on the board. For more information, see Texas Instruments literature numbers SLMA002 (www.ti.com/lit/slma002) and SLMA004 (www.ti.com/lit/slma004).
- 8. Size of metal pad may vary due to creepage requirement.
- 9. Vias are optional depending on application, refer to device data sheet. It is recommended that vias under paste be filled, plugged or tented.




# **PWP0016J**

# **EXAMPLE STENCIL DESIGN**

# PowerPAD<sup>™</sup> TSSOP - 1.2 mm max height

SMALL OUTLINE PACKAGE



10. Laser cutting apertures with trapezoidal walls and rounded corners may offer better paste release. IPC-7525 may have alternate design recommendations.

11. Board assembly site may have different recommendations for stencil design.



#### **IMPORTANT NOTICE**

Texas Instruments Incorporated (TI) reserves the right to make corrections, enhancements, improvements and other changes to its semiconductor products and services per JESD46, latest issue, and to discontinue any product or service per JESD48, latest issue. Buyers should obtain the latest relevant information before placing orders and should verify that such information is current and complete.

TI's published terms of sale for semiconductor products (http://www.ti.com/sc/docs/stdterms.htm) apply to the sale of packaged integrated circuit products that TI has qualified and released to market. Additional terms may apply to the use or sale of other types of TI products and services.

Reproduction of significant portions of TI information in TI data sheets is permissible only if reproduction is without alteration and is accompanied by all associated warranties, conditions, limitations, and notices. TI is not responsible or liable for such reproduced documentation. Information of third parties may be subject to additional restrictions. Resale of TI products or services with statements different from or beyond the parameters stated by TI for that product or service voids all express and any implied warranties for the associated TI product or service and is an unfair and deceptive business practice. TI is not responsible or liable for any such statements.

Buyers and others who are developing systems that incorporate TI products (collectively, "Designers") understand and agree that Designers remain responsible for using their independent analysis, evaluation and judgment in designing their applications and that Designers have full and exclusive responsibility to assure the safety of Designers' applications and compliance of their applications (and of all TI products used in or for Designers' applications) with all applicable regulations, laws and other applicable requirements. Designer represents that, with respect to their applications, Designer has all the necessary expertise to create and implement safeguards that (1) anticipate dangerous consequences of failures, (2) monitor failures and their consequences, and (3) lessen the likelihood of failures that might cause harm and take appropriate actions. Designer agrees that prior to using or distributing any applications that include TI products, Designer will thoroughly test such applications and the functionality of such TI products as used in such applications.

TI's provision of technical, application or other design advice, quality characterization, reliability data or other services or information, including, but not limited to, reference designs and materials relating to evaluation modules, (collectively, "TI Resources") are intended to assist designers who are developing applications that incorporate TI products; by downloading, accessing or using TI Resources in any way, Designer (individually or, if Designer is acting on behalf of a company, Designer's company) agrees to use any particular TI Resource solely for this purpose and subject to the terms of this Notice.

TI's provision of TI Resources does not expand or otherwise alter TI's applicable published warranties or warranty disclaimers for TI products, and no additional obligations or liabilities arise from TI providing such TI Resources. TI reserves the right to make corrections, enhancements, improvements and other changes to its TI Resources. TI has not conducted any testing other than that specifically described in the published documentation for a particular TI Resource.

Designer is authorized to use, copy and modify any individual TI Resource only in connection with the development of applications that include the TI product(s) identified in such TI Resource. NO OTHER LICENSE, EXPRESS OR IMPLIED, BY ESTOPPEL OR OTHERWISE TO ANY OTHER TI INTELLECTUAL PROPERTY RIGHT, AND NO LICENSE TO ANY TECHNOLOGY OR INTELLECTUAL PROPERTY RIGHT OF TI OR ANY THIRD PARTY IS GRANTED HEREIN, including but not limited to any patent right, copyright, mask work right, or other intellectual property right relating to any combination, machine, or process in which TI products or services are used. Information regarding or referencing third-party products or services does not constitute a license to use such products or services, or a warranty or endorsement thereof. Use of TI Resources may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

TI RESOURCES ARE PROVIDED "AS IS" AND WITH ALL FAULTS. TI DISCLAIMS ALL OTHER WARRANTIES OR REPRESENTATIONS, EXPRESS OR IMPLIED, REGARDING RESOURCES OR USE THEREOF, INCLUDING BUT NOT LIMITED TO ACCURACY OR COMPLETENESS, TITLE, ANY EPIDEMIC FAILURE WARRANTY AND ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, AND NON-INFRINGEMENT OF ANY THIRD PARTY INTELLECTUAL PROPERTY RIGHTS. TI SHALL NOT BE LIABLE FOR AND SHALL NOT DEFEND OR INDEMNIFY DESIGNER AGAINST ANY CLAIM, INCLUDING BUT NOT LIMITED TO ANY INFRINGEMENT CLAIM THAT RELATES TO OR IS BASED ON ANY COMBINATION OF PRODUCTS EVEN IF DESCRIBED IN TI RESOURCES OR OTHERWISE. IN NO EVENT SHALL TI BE LIABLE FOR ANY ACTUAL, DIRECT, SPECIAL, COLLATERAL, INDIRECT, PUNITIVE, INCIDENTAL, CONSEQUENTIAL OR EXEMPLARY DAMAGES IN CONNECTION WITH OR ARISING OUT OF TI RESOURCES OR USE THEREOF, AND REGARDLESS OF WHETHER TI HAS BEEN ADVISED OF THE POSSIBILITY OF SUCH DAMAGES.

Unless TI has explicitly designated an individual product as meeting the requirements of a particular industry standard (e.g., ISO/TS 16949 and ISO 26262), TI is not responsible for any failure to meet such industry standard requirements.

Where TI specifically promotes products as facilitating functional safety or as compliant with industry functional safety standards, such products are intended to help enable customers to design and create their own applications that meet applicable functional safety standards and requirements. Using products in an application does not by itself establish any safety features in the application. Designers must ensure compliance with safety-related requirements and standards applicable to their applications. Designer may not use any TI products in life-critical medical equipment unless authorized officers of the parties have executed a special contract specifically governing such use. Life-critical medical equipment is medical equipment where failure of such equipment would cause serious bodily injury or death (e.g., life support, pacemakers, defibrillators, heart pumps, neurostimulators, and implantables). Such equipment includes, without limitation, all medical devices identified by the U.S. Food and Drug Administration as Class III devices and equivalent classifications outside the U.S.

TI may expressly designate certain products as completing a particular qualification (e.g., Q100, Military Grade, or Enhanced Product). Designers agree that it has the necessary expertise to select the product with the appropriate qualification designation for their applications and that proper product selection is at Designers' own risk. Designers are solely responsible for compliance with all legal and regulatory requirements in connection with such selection.

Designer will fully indemnify TI and its representatives against any damages, costs, losses, and/or liabilities arising out of Designer's noncompliance with the terms and provisions of this Notice.

> Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265 Copyright © 2017, Texas Instruments Incorporated