OSRAM GF CS8PM2.24 Datasheet

Not for new design

Published by ams-OSRAM AG Tobelbader Strasse 30, 8141 Premstaetten, Austria Phone +43 3136 500-0 ams-osram.com © All rights reserved






OSLON® SSL 80

GF CS8PM2.24

New, higher performing OSLON SSL family LED with well known superior robustness, high reliability, long lifetime, low thermal resistance. Perfectly addressing applications demanding for high efficiency and long lifetime requirement.





Applications

- Architecture

- Horticulture Lighting

Features

- Package: SMT ceramic package with silicone lens
- Typ. Radiation: 80°
- Corrosion Robustness Class: 3B
- ESD: 8 kV acc. to ANSI/ESDA/JEDEC JS-001 (HBM, Class 3B)
- Radiant Flux: typ. 365 mW
- Radiant Efficiency : typ. 56 %



Ordering Information

Туре	Total radiant flux ¹⁾ Ι _F = 350 mA Φ _E	Ordering Code
GF CS8PM2.24-2T4T-1	315 450 mW	Q65112A8358



Maximum Ratings

Parameter	Symbol		Values
Operating Temperature	T _{op}	min. max.	-40 °C 120 °C
Storage Temperature	T_{stg}	min. max.	-40 °C 120 °C
Junction Temperature	Tj	max.	125 °C
Forward current	I _F	min. max.	100 mA 1000 mA
Surge Current t ≤ 10 µs; D = 0.005 ; T _J = 25 °C	I _{FS}	max.	2000 mA
Reverse current ²⁾	I _R	max.	200 mA
ESD withstand voltage acc. to ANSI/ESDA/JEDEC JS-001 (HBM, Class 3B)	V_{ESD}		8 kV



Characteristics

I_F = 350 mA; T_J = 25 °C

Parameter	Symbol		Values	
Peak Wavelength	λ_{peak}	typ.	730 nm	
Centroid Wavelength ³⁾	$\lambda_{centroid}$	min.	710 nm	
I ₌ = 350 mA	centiola	typ.	727 nm	
		max.	740 nm	
Spectral Bandwidth at 50% I _{rel,max}	Δλ	typ.	30 nm	
Viewing angle at 50% I_v	2φ	typ.	° 08	
Forward Voltage 4)	V _F	min.	1.60 V	
I ₌ = 350 mA		typ.	1.85 V	
		max.	2.30 V	
Reverse voltage 2)	V _R	max.	1.2 V	
I _R = 20 mA				
Electrical thermal resistance junction/solderpoint with efficiency $\eta_{\rm e}$ = 43 %	$R_{thJSelec.}$	typ.	3.5 K / W	



Brightness Groups

Group	Total radiant flux ¹⁾ I _E = 350 mA	Total radiant flux ¹⁾ I _E = 350 mA	PPF *	PPF *	PPF/W *	PF **	PF **	PF/W **
	min. Φ _ε	max. Φ _ε	min. Φ _ρ	max. Φ _ρ	typ.	min. Φ _{p,b}	max. Φ _{p,b}	typ.
2T	315 mW	355 mW	0.25 µmol/s	0.29 µmol/s	0.39 µmol/J	1.89 µmol/s	2.13 µmol/s	2.95 µmol/J
3T	355 mW	400 mW	0.29 µmol/s	0.32 µmol/s	0.44 µmol/J	2.13 µmol/s	2.40 µmol/s	3.32 µmol/J
4T	400 mW	450 mW	0.32 µmol/s	0.36 µmol/s	0.50 µmol/J	2.40 µmol/s	2.70 µmol/s	3.74 µmol/J

Note: [*] Photosynthetic Photon Flux includes wavelengths between 400 and 700 nm Note: [**] Photon Flux includes wavelengths between 280 and 800 nm Note: PPF and PF values are for reference only

Centroid Wavelength

Group	Centroid Wavelength ³⁾	Centroid Wavelength ³⁾	
	I _F = 350 mA	l _F = 350 mA	
	min.	max.	
_	$\lambda_{centroid}$	$\lambda_{ ext{centroid}}$	
1	710 nm	740 nm	




Group Name on Label

Example: 2T-1 Brightness	Wavelength
2T	1




Relative Spectral Emission ⁵⁾

 $I_{rel} = f(\lambda); I_{F} = 350 \text{ mA}; T_{J} = 25 \text{ }^{\circ}\text{C}$



Radiation Characteristics ⁵⁾


 $I_{rel} = f(\phi); T_J = 25 \ ^{\circ}C$






Forward current ⁵⁾

 $I_F = f(V_F); T_J = 25 \ ^{\circ}C$



Relative Radiant Power 5), 6)


 $\Phi_{\rm E}/\Phi_{\rm E}(350 \text{ mA}) = f(I_{\rm F}); T_{\rm J} = 25 \text{ °C}$






Forward Voltage ⁵⁾

 $\Delta V_{_F} = V_{_F} - V_{_F}(25 \text{ °C}) = f(T_{_J}); I_{_F} = 350 \text{ mA}$



Relative Radiant Power⁵⁾

 $\Phi_{_{\rm E}}/\Phi_{_{\rm E}}(25 \ ^{\circ}{\rm C}) = f(T_{_{\rm i}}); I_{_{\rm F}} = 350 \text{ mA}$




Centroid Wavelength ⁵⁾

 $\Delta \lambda_{centr} = \lambda_{centr} - \lambda_{centr} (25 \text{ °C}) = f(T_j); I_F = 350 \text{ mA}$ $\Delta \lambda_{centr} / \text{ nm} \stackrel{15}{}_{0} \stackrel{\text{GF CS8PM2.24}}{}_{0} \stackrel{1}{}_{0} \stackrel{1}{}$




Max. Permissible Forward Current

 $I_{_{\rm F}} = f(T)$







Dimensional Drawing 7)



General tolerance ±0.1 Lead finish Au






C67062-A0181-A4-01

Further Information:

Approximate Weight:	24.0 mg
Package marking:	Anode
Corrosion test:	Class: 3B Test condition: 40°C / 90 % RH / 15 ppm H ₂ S / 14 days (stricter than IEC 60068-2-43)
ESD advice:	The device is protected by ESD device which is connected in parallel to the Chip.




Recommended Solder Pad 7)




For superior solder joint connectivity results we recommend soldering under standard nitrogen atmosphere. Further information can be found in our Application Note: "Handling and Processing Details for Ceramic LEDs".



Reflow Soldering Profile






Profile Feature	Symbol	Pb	-Free (SnAgCu) Ass	Unit	
		Minimum	Recommendation	Maximum	
Ramp-up rate to preheat ^{•)} 25 °C to 150 °C			2	3	K/s
Time t _s T _{smin} to T _{smax}	t _s	60	100	120	S
Ramp-up rate to peak ^{*)} T_{smax} to T_{p}			2	3	K/s
Liquidus temperature	TL		217		°C
Time above liquidus temperature	t		80	100	S
Peak temperature	Τ _Ρ		245	260	°C
Time within 5 °C of the specified peak temperature T_p - 5 K	t _P	10	20	30	S
Ramp-down rate* T _P to 100 °C			3	6	K/s
Time 25 °C to T _P				480	S

All temperatures refer to the center of the package, measured on the top of the component * slope calculation DT/Dt: Dt max. 5 s; fulfillment for the whole T-range




Taping 7)





Tape and Reel⁸⁾




Reel Dimensions


А	W	N _{min}	W ₁	$W_{2\text{max}}$	Pieces per PU
180 mm	12 + 0.3 / - 0.1 mm	60 mm	12.4 + 2 mm	18.4 mm	600



Barcode-Product-Label (BPL)



Dry Packing Process and Materials 7)



Moisture-sensitive product is packed in a dry bag containing desiccant and a humidity card according JEDEC-STD-033.



Notes

The evaluation of eye safety occurs according to the standard IEC 62471:2006 (photo biological safety of lamps and lamp systems). Within the risk grouping system of this IEC standard, the device specified in this data sheet fall into the class **exempt group (exposure time 10000 s)**. Under real circumstances (for exposure time, conditions of the eye pupils, observation distance), it is assumed that no endangerment to the eye exists from these devices. As a matter of principle, however, it should be mentioned that intense light sources have a high secondary exposure potential due to their blinding effect. When looking at bright light sources (e.g. headlights), temporary reduction in visual acuity and afterimages can occur, leading to irritation, annoyance, visual impairment, and even accidents, depending on the situation.

Subcomponents of this device contain, in addition to other substances, metal filled materials including silver. Metal filled materials can be affected by environments that contain traces of aggressive substances. Therefore, we recommend that customers minimize device exposure to aggressive substances during storage, production, and use. Devices that showed visible discoloration when tested using the described tests above did show no performance deviations within failure limits during the stated test duration. Respective failure limits are described in the IEC60810.

This device is designed for specific/recommended applications only. Please consult OSRAM Opto Semiconductors Sales Staff in advance for detailed information on other non-recommended applications (e.g. automotive).

Change management for this component is aligned with the requirements of the lighting market.

For further application related information please visit www.osram-os.com/appnotes



Disclaimer

Attention please!

The information describes the type of component and shall not be considered as assured characteristics. Terms of delivery and rights to change design reserved. Due to technical requirements components may contain dangerous substances.

For information on the types in question please contact our Sales Organization.

If printed or downloaded, please find the latest version on our website.

Packing

Please use the recycling operators known to you. We can also help you – get in touch with your nearest sales office. By agreement we will take packing material back, if it is sorted. You must bear the costs of transport. For packing material that is returned to us unsorted or which we are not obliged to accept, we shall have to invoice you for any costs incurred.

Product and functional safety devices/applications or medical devices/applications

Our components are not developed, constructed or tested for the application as safety relevant component or for the application in medical devices.

Our products are not qualified at module and system level for such application.

In case buyer – or customer supplied by buyer – considers using our components in product safety devices/ applications or medical devices/applications, buyer and/or customer has to inform our local sales partner immediately and we and buyer and /or customer will analyze and coordinate the customer-specific request between us and buyer and/or customer.



Glossary

- ¹⁾ **Brightness:** Brightness values are measured during a current pulse of typically 10 ms, with a tolerance of +/- 7%.
- ²⁾ Reverse Operation: This product is intended to be operated applying a forward current within the specified range. Applying any continuous reverse bias or forward bias below the voltage range of light emission shall be avoided because it may cause migration which can change the electro-optical characteristics or damage the LED.
- ³⁾ Wavelength: The wavelength is measured at a current pulse of typically 10 ms, with a tolerance of ± 0.5 nm.
- ⁴⁾ **Forward Voltage:** The Forward voltage is measured during a current pulse duration of typically 1 ms with a tolerance of ± 0.05V.
- ⁵⁾ Typical Values: Due to the special conditions of the manufacturing processes of semiconductor devices, the typical data or calculated correlations of technical parameters can only reflect statistical figures. These do not necessarily correspond to the actual parameters of each single product, which could differ from the typical data and calculated correlations or the typical characteristic line. If requested, e.g. because of technical improvements, these typ. data will be changed without any further notice.
- ⁶⁾ **Characteristic curve:** In the range where the line of the graph is broken, you must expect higher differences between single devices within one packing unit.
- ⁷⁾ **Tolerance of Measure:** Unless otherwise noted in drawing, tolerances are specified with ±0.1 and dimensions are specified in mm.
- ⁸⁾ **Tape and Reel:** All dimensions and tolerances are specified acc. IEC 60286-3 and specified in mm.



Revision History

Version	Date	Change	
1.14	2019-03-08	Features Ordering Information Brightness Groups	
1.15	2019-04-16	Ordering Information Brightness Groups	
1.15	2019-05-10	Features Characteristics	
1.15	2020-03-11	Schematic Transportation Box Dimensions of Transportation Box	
1.16	2021-08-17	Features Characteristics Electro - Optical Characteristics (Diagrams)	
1.17	2022-04-05	Not for new design	

Not for new design



EU RoHS and China RoHS compliant product 此产品符合欧盟 RoHS 指令的要求; 按照中国的相关法规和标准, 不含有毒有害物质或元素。

Published by ams-OSRAM AG Tobelbader Strasse 30, 8141 Premstaetten, Austria Phone +43 3136 500-0 ams-osram.com © All rights reserved

