

LOW EMI CURRENT SENSE HIGH SIDE SWITCH

Features

- Load current feedback
- Over current shutdown
- Active clamp
- ESD protection
- Input referenced to Vcc
- Over temperature shutdown
- Switching time optimized for low EMI
- · Reverse battery protection

Description

The AUIR3317(S) is a fully protected 4 terminals high side switch. The input signal is referenced to Vcc. When the input voltage Vcc - Vin is higher than the specified threshold, the output power Mosfet is turned on. When the Vcc - Vin is lower than the specified Vil threshold, the output Mosfet is turned off. A current proportional to the power Mosfet current is sourced to the Ifb pin. Either over current and over temperature latches off the switch. The device is reset by pulling the input pin high. Other integrated protections (ESD, reverse battery, active clamp) make the switch very rugged in automotive environment.


Product Summary

Rds(on)	7 m Ω max.
Vcc op.	6 to 26V
Current Ratio	8800
Over-current	120A
Vclamp	40V

Package



Typical Connection





Qualification Information[†]

<u>taaiiiio</u>						
		Automotive (per AEC-Q100 ^{††})				
Qualificat	ion Level	Comments: This family of ICs has passed an Automotive qualification. Il Industrial and Consumer qualification level is granted by extension of higher Automotive level.				
Moisture Sensitivity Level		D2PAK-5L	MSL1, 260°C (per IPC/JEDEC J-STD-020)			
molocuro	Condition, 2000.	TO220-5L	Not applicable			
	Machine Model	Class M4 (450V) (per AEC-Q100-003)				
ESD	Human Body Model	Class H3A (4 (per AEC-Q1	,			
	Charged Device Model	Class C4 (1000 V) (per AEC-Q100-011)				
IC Latch-	Up Test	Class II, Level A (per AEC-Q100-004)				
RoHS Co	mpliant	Yes				

[†] Qualification standards can be found at International Rectifier's web site http://www.irf.com/

^{††} Exceptions to AEC-Q100 requirements are noted in the qualification report.



Absolute Maximum Ratings

Absolute maximum ratings indicate sustained limits beyond which damage to the device may occur. All voltage parameters are referenced to Vcc lead. (Tj=-40°..150°C, Vcc=6..26V Tambient=25°C unless otherwise specified).

Symbol	Parameter	Min.	Max.	Units
Vcc-Vin	Maximum Vcc voltage	-16	37	
Vcc-Vin cont.	Maximum continuous Vcc voltage	-16	26	V
Vcc-Vfb	Maximum Ifb voltage	-16	33	V
Vcc-Vout	Maximum output voltage	-0.3	37	
lds cont.	Maximum body diode continuous current Rth=60°C/W (1) Tambient=25°C	_	2.8	Α
lds pulsed	Maximum body diode pulsed current (1)	_	100	^
Pd	Maximum power dissipation Rth=60°C/W Tambient=25°C	_	2	W
Tj max.	Max. storage & operating temperature junction temperature	-40	150	°C
Min Rfb	Minimum on the resistor on Ifb pin	0.3	_	kΩ
Ifb max.	Max. Ifb current	-50	50	mA

⁽¹⁾ Limited by junction temperature. Pulsed is also limited by wiring

Thermal Characteristics

Symbol	Parameter	Тур.	Max.	Units
Rth1	Thermal resistance junction to ambient D²-Pak Std footprint	60	_	
Rth2	Thermal resistance junction to case D²-Pak	0.7	_	°C/W
Rth2	Thermal resistance junction to case TO220	0.7	_	

Recommended Operating Conditions

These values are given for a quick design. For operation outside these conditions, please consult the application notes.

Symbol	Parameter	Min.	Max.	Units
lout	Continuous output current			
	Tambient=85°C, Rth=5°C/W, Tj=125°C		23	Α
	Tambient=85°C, Rth=60°C/W, Tj=125°C] —	7	
Pulse min.	Minimum turn-on pulse width	1	_	ms
Fmax.	Maximum operating frequency		200	Hz



Protection Characteristics

Tj=-40°..150°C, Vcc=6..26V

Symbol	Parameter	Min.	Тур.	Max.	Units	Test Conditions
Tsd	Over temperature threshold	_	165	_	°C	See fig. 5
OV	Over voltage protection (not latched)	26	29	33	V	
Isdf	Fixed over current shutdown	90	120	150	Α	Vcc-Vifb>4V(3)
treset	Time to reset protection	_	50	500	0	See fig. 5
Min. pulse	Min. pulse width (no WAIT state)	_	900	2000	μs	Tj=25°C
WAIT	WAIT function timer	0.4	1	2	ms	See fig. 4 and 5
Rds(on) rev.	Reverse battery On state resistance	4	6.7	10		Vcc-Vin=-14V,
	Tj=25°C				mΩ	lout=30A
	TJ=125°C	_	10	15		

⁽³⁾ With Vcc-Vifb<4V, the Isdf is lower than specified in the datasheet

Static Electrical Characteristics

Ti=-40°..150°C. Vcc=6..26V (unless otherwise specified)

Symbol	Parameter	Min.	Тур.	Max.	Units	Test Conditions
Vcc op.	Operating Voltage range	6		26	V	
Icc off	Supply leakage current		1.5	5	μA	Vin=Vcc, Vcc-Vout=14V, Vcc-Vifb=14V, Tj=25°C
lin, on	On state IN positive current	1.5	3	6	mA	Vcc-Vin=14V, Tj=25°C
Vih	High level Input threshold voltage (4)	T —	5.4	6.3		
Vil	Low level Input threshold voltage (4)	4	4.9	5.8	V	
Vhyst	Input hysteresis Vih-Vil	0.2	0.4	1.5		
lout	Drain to source leakage current	_	1.2	5	μA	Vin=Vcc, Vcc-Vifb=0V, Vcc-Vout=14V, Tj=25°C
Rds(on)	On state resistance (5) Tj=25°C	4	5.5	7		lout=30A, Vcc-Vin=14V
	On state resistance (5) Tj=25°C	4	6	10	mΩ	lout=17A, Vcc-Vin=6V
	On state resistance (5)(6) Tj=150°C	7	10.5	13.5]	Iout=30A, Vcc-Vin=14V
V clamp1	Vcc to Vout clamp voltage 1	36	39	_	V	Iout=50mA
V clamp2	Vcc to Vout clamp voltage 2		40	43	ľ	lout=30A, Tj=25°C

⁽⁴⁾ Input thresholds are measured directly between the input pin and the tab. Any parasitic resistance in common between the load current path and the input signal path can significantly affect the thresholds.

Switching Electrical Characteristics

Vcc=14V, Resistive load=0.5Ω, Tj=25°C

Symbol	Parameter	Min.	Тур.	Max.	Units	Test Conditions
tdon	Turn on delay time to 10% Vcc	30	120	300		
tr1	Rise time to Vcc-Vout=5V	20	50	125	μs	
tr2	Rise time to Vcc-Vout=0.1Vcc	30	80	200		
Eon	Turn on energy	_	14	_	mJ	See figure 2
tdoff	Turn off delay time	30	140	350	0	
tf	Fall time to Vout=10% of Vcc	35	100	250	μs	
Eoff	Turn off energy		7	_	mJ	

⁽⁵⁾ Rdson is measured between the tab and the Out pin, 5mm away from the package.


⁽⁶⁾ Guaranteed by design

Current Sense Characteristics


Tj=-40°..150°C, Vcc=6..26V (unless otherwise specified)


Symbol	Parameter	Min.	Тур.	Max.	Units	Test Conditions
Ratio	I Load/lifb current ratio	8,200	8,800	9,950	_	Rfb=500Ω, Iout=60A
Ratio_TC	I Load/lifb variation aver temperature(6)	-5	_	+5	%	Tj=-40°C to 150°C
Offset	Load current diagnostic offset	-0.2	0	+0.25	Α	lout=2A
trst	Ifb response time (low signal)	_	1	_	μs	90% of the lout step

Functional Block Diagram



Lead Assignments









Figure 1 - Voltages and current definitions

Figure 2 – Switching time definitions








Figure 3 – Active clamp waveforms

Figure 4 - Min. pulse and Wait function




Figure 5 – Protection Timing Diagrams



All curves are typical characteristics. Operation in hatched areas is not recommended. Tj=25°C, Rifb=500ohm, Vcc=14V (unless otherwise specified).





Figure 6 - Icc (mA) Vs Vcc-Vin (V)

Figure 7 – Icc off (µA) Vs Tj (°C)








Figure 9 - Vih and Vil (V) Vs Tj (°C)






Figure 10 - Error (+/- A) Vs I load (A)





Figure 12 - Max. lout (A) Vs Tamb. (°C)



Rifb, feedback resistor (Ω)

Figure 11 – Ids (A) Vs Rifb (Ω)





Figure 13 - Max. lout (A) Vs inductance (µH)









Figure 14 – Ids (A) Vs over temperature protection response time (s)


Figure 15 – Transient thermal impedance (°C/W) Vs time (s)


Case Outline - TO220 - 5 Leads













- DIMENSIONING AND TOLERANCING AS PER ASME Y14.5 M— 1994.
 DIMENSIONS ARE SHOWN IN INCHES [MILLIMETERS].
 LEAD DIMENSION AND FIRSH UNCONTROLLED IN 1.1
 DIMENSION, D. In & E DO NOT INCLIDE MOLD FLASH MOLD FLASH
 SHALL NOT EXCEDS JOS¹ (0.127) PER SIDE THESE DIMENSIONS AND
 MEASURED AT THE OUTERWISE STREEMEDS OF THE PLASTIC BOOY.
 DIMENSION IS A E1 APPLY TO BASE METAL ONLY.
 CONTROLLING DIMENSION IS MORE STREEMEDS OF THE PLASTIC BOOY.
 DIMENSION ES LET HE DEFINE A DOME WHERE STAPPING
 AND SINGULATION REPOLLARITIES ARE ALLOWED.
 OUTLINE CONFORMS TO JUEDE OF 1-202, DIMED TA & (max.) AND D.2 (mix.)
 WHERE DIMENSIONS ARE DERIVED FROM THE ACTUAL PACKAGE OUTLINE.


10.- LEADS AND DRAIN ARE PLATED WITH 100% Sn




Case Outline - D2PAK - 5 leads











Y M			N		
В	MILLIM	ETERS	INC	HES	Ö
P.	MIN.	MAX.	MIN.	MAX.	Ë
Α	4.06	4.83	.160	.190	
A1		0.254		.010	
ь	0.66	0.91	.026	.036	4
ь1	0.66	0.81	.026	.032	
c	0.38	0.74	.015	.029	
c1	0.38	0.58	.015	.023	4
c2	1.14	1.65	.045	.065	
D	8.51	9.65	.335	.380	3
D1	6.86		.270		
Ε	9.65	10.67	.380	.420	3
E1	6.22		.245		
e	1.70	BSC	.067	BSC]
н	14.73	15.49	.580	.609	1
L	1.14	1.39	.045	.055	
L1		1.65		.065	
L2	1.27	1.78	.050	.070	
L3	0.25	BSC	.010	BSC]
L4	4.78	5.28	.188	.208]
m	17.78		.700		
m1	8.89		.350		
n	11.43		.450		
0	1.93		.076		
P	3.81		.150		
R	0.51	0.71	.020	.028	\Box






c2
^-
DETAIL A
c—= - //[±.004@ B

- 1. DIMENSIONING AND TOLERANCING PER ASME Y14.5M-1994
- 2. DIMENSIONS ARE SHOWN IN MILLIMETERS [INCHES].
- DIMENSION D & E DO NOT INCLUDE MOLD FLASH, MOLD FLASH SHALL NOT EXCEED 0.127 [.005*] PER SIDE. THESE DIMENSIONS ARE MEASURED AT THE OUTMOST EXTREMES OF THE PLASTIC BODY.

ADIMENSION b1 AND c1 APPLY TO BASE METAL ONLY.


- 5. CONTROLLING DIMENSION: MILLIMETERS
- 6. LEADS AND DRAIN ARE PLTED WITH 100% Sn

Tape & Reel - D2PAK - 5 leads





Part Marking Information



Ordering Information

Base Part Number		Standard Pack	0 14 5 4 11 1	
base Fait Number	Package Type	Form	Quantity	Complete Part Number
	TO220 - 5Leads	Tube	50	AUIR3317
AUIR3317	D2Pak – 5Leads	Tube	50	AUIR3317S
AUR3317		Tape and reel left	800	AUIR3317STRL
		Tape and reel right	800	AUIR3317STRR



IMPORTANT NOTICE

Unless specifically designated for the automotive market, International Rectifier Corporation and its subsidiaries (IR) reserve the right to make corrections, modifications, enhancements, improvements, and other changes to its products and services at any time and to discontinue any product or services without notice. Part numbers designated with the "AU" prefix follow automotive industry and / or customer specific requirements with regards to product discontinuance and process change notification. All products are sold subject to IR's terms and conditions of sale supplied at the time of order acknowledgment.

IR warrants performance of its hardware products to the specifications applicable at the time of sale in accordance with IR's standard warranty. Testing and other quality control techniques are used to the extent IR deems necessary to support this warranty. Except where mandated by government requirements, testing of all parameters of each product is not necessarily performed.

IR assumes no liability for applications assistance or customer product design. Customers are responsible for their products and applications using IR components. To minimize the risks with customer products and applications, customers should provide adequate design and operating safeguards.

Reproduction of IR information in IR data books or data sheets is permissible only if reproduction is without alteration and is accompanied by all associated warranties, conditions, limitations, and notices. Reproduction of this information with alterations is an unfair and deceptive business practice. IR is not responsible or liable for such altered documentation. Information of third parties may be subject to additional restrictions.

Resale of IR products or serviced with statements different from or beyond the parameters stated by IR for that product or service voids all express and any implied warranties for the associated IR product or service and is an unfair and deceptive business practice. IR is not responsible or liable for any such statements.

IR products are not designed, intended, or authorized for use as components in systems intended for surgical implant into the body, or in other applications intended to support or sustain life, or in any other application in which the failure of the IR product could create a situation where personal injury or death may occur. Should Buyer purchase or use IR products for any such unintended or unauthorized application, Buyer shall indemnify and hold International Rectifier and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that IR was negligent regarding the design or manufacture of the product.

Only products certified as military grade by the Defense Logistics Agency (DLA) of the US Department of Defense, are designed and manufactured to meet DLA military specifications required by certain military, aerospace or other applications. Buyers acknowledge and agree that any use of IR products not certified by DLA as military-grade, in applications requiring military grade products, is solely at the Buyer's own risk and that they are solely responsible for compliance with all legal and regulatory requirements in connection with such use.

For technical support, please contact IR's Technical Assistance Center http://www.irf.com/technical-info/

WORLD HEADQUARTERS:

101 N. Sepulveda Blvd., El Segundo, California 90245 Tel: (310) 252-7105

Revision History

Revision	Date	Notes/Changes
Α		First release
В	10/06/2010	AU release
С	25/08/2011	Add test condition to Isdf page 4