

SPECIFICATION SHEET

| SPECIFICATION SHEET NO. | Q0216- 1T228M025HJHBA |
|-------------------------|---|
| DATE | Feb. 16, 2023 |
| REVISION | A0 |
| DESCRIPITION | Through Hole Standard Aluminum Electrolytic Capacitors, Radial Type 1T series, 2 Pins, Case size: Ø13.0*L25.0mm, Sleeve: PET, Capacitance: 2200μF, Tolerance ±20%, Voltage 25V, Ripple Current 1110 mA Max. @+105°C, 120Hz Lifetime 2000Hours @105°C, Operating Temp. Range -55°C ~+105°C. RoHS/RoHS III Compliant & Halogen Free Package in Bulk, 200pcs/Bag |
| CUSTOMER | |
| CUSTOMER PART NUMBER | |
| CROSS REF. PART NUMBER | |
| ORIGINAL PART NUMBER | Aillen CBE228M1EHJAJ25RR |
| PART CODE | 1Т228М025НЈНВА |

| VENDOR APPROVE | | | |
|-------------------------|-------------------------------------|---------------|-------------------------|
| lssued/Checked/Approved | Component Mandy Xu Toyyerv | Ruby Zhang | Jack zhang traves |
| DATE: Feb. 16, 2023 | | | |

CUSTOMER APPROVE
DATE:
2/16/2023 1



DIP ALUMINUM ELECTROLYTIC CAPACITORS 1T SERIES

MAIN FEATURE

- Through Hole Standard Aluminum Electrolytic Capacitors, Radial Type
- Long Load Life
- RoHS Complaint And Halogen Free
- Tape Package And Lead Cut 3.5~7.0mm Optional

APPLICATION

• For Standard Circuit Like Coupling Filter And Energy Storage Etc.

PART CODE GUIDE

| 1T | 228 | м | 025 | н | J | н | В | Α |
|----|-----|---|-----|---|---|---|---|---|
| 1 | 2 | 3 | 4 | 5 | 6 | 7 | 8 | 9 |

1) 1T: Through Hole Standard Aluminum Electrolytic Capacitors, Radial Type, 1T series

2) 228: Rated Capacitance Code, 105: 1.0µF; 225: 2.2µF; 335: 3.3µF; 475: 4.7µF; 685: 6.8µF; 106: 10µF; 226: 22µF; 336: 33µF;

476: 47µF; 686: 68µF; 107: 100µF; 227: 220µF; 337: 330µF; 477: 470µF; **228: 2200µF**; 338: 3300µF

3) M: Capacitance tolerance code, M: ±20%; V: -10% ~ ±20%; R: -0~ ±20%

4) 025: Rated Voltage Code, 6V3: 6.3V; 010: 10V; 016:16V; 025: 25V; 035: 35V; 050: 50V; 063: 63V; 100: 100V; 160: 160V

200: 200V; 250: 250V; 350: 350V; 400: 400V; 450V: 450V


- 5) H: Environmental Requirements code, R: RoHS Complaint (PVS Sleeve); H: RoHS III Complaint & Halogen Free (PET Sleeve)
- 6) J: Aluminum Case size code, D: Ø5.0mm; E: Ø6.3mm; F: Ø8.0mm; G: Ø10.0mm; I: Ø12.5mm; J: Ø13.0mm; K: Ø16.0mm
 - L: Ø18.0mm; N: Ø22.0mm
- 7) C: Aluminum case Heigh code, A: L11mm; B: L11.5mm; C: L12mm; D: L12.5mm; E: L20mm; F: L21.5mm; G: L31.5mm; H:25mm
- 8) B: Package in Bulk, 200pcs/Bag
- 9) A: Internal control or Special Code (A~Z or 1~9)

2/20/2023










DIP ALUMINUM ELECTROLYTIC CAPACITORS 1T SERIES



1T Series

Case Ø13.0*L25mm



| Symbol | D | F | d | L | α |
|----------------|-------|-----|-------|----------|-----|
| Dimension (mm) | Ø13.0 | 5.0 | Ø0.60 | 25.0+/-α | 2.0 |

Marking:

Unless otherwise specified. Capacitor


shall be clearly marked on it body.

Casing Type


Sleeve and printing color:

White Printing on black Sleeve

| Brand | Aillen |
|------------------------|------------------------------|
| Polarity | $ \rightarrow \rightarrow $ |
| Nominal capacitance | 2200µF |
| Rated voltage | 25V |
| Original Series | CDJA |
| Temperature Range | -55~+105°C |




2/20/2023




DIP ALUMINUM ELECTROLYTIC CAPACITORS 1T SERIES

CONSTRUCTION

Single ended type to be produced to fix the terminals to anode and cathode foil, and wind together with paper, and then wound element to be impregnated with electrolyte will be enclosed in an aluminum case. Finally sealed up tightly with end seal rubber, then finished by putting on the vinyl sleeve.



| No. | Component | Material |
|-----|------------------|--|
| 1 | Lead Line | Tinned CP Wire (Pb Free) |
| 2 | Terminal | Aluminum Wire |
| 3 | Sealing Material | Rubber |
| 4 | Al-Foil (+) | Formed Aluminum Foil |
| 5 | Al-Foil (-) | Etched aluminum foil or formed Aluminum Foil |
| 6 | Case | Aluminum case |
| 7 | Sleeve | PET |
| 8 | Separator | Electrolyte paper |



DIP ALUMINUM ELECTROLYTIC CAPACITORS 1T SERIES

CHARACTERISTICS

Standard atmospheric conditions

The standard range of atmospheric conditions for making measurements/test as follows:

Ambient temperature: 15°C to 35°C

Relative humidity: 45% to 85%

Air Pressure: 86kPa to 106kPa

If there is any doubt about the results, measurement shall be made within the following conditions:

Ambient temperature: 20°C \pm 2°C

Relative humidity: 60% to 70%


Air Pressure: 86kPa to 106kPa

As to the detailed information, please refer to following Table 1 and Table 2

Table 1

| ITEM | CHARACTERISTICS |
|-----------------------------|-----------------|
| Operating Temperature Range | -55~+105°C |
| Rated Voltage Range | 25 V |
| Capacitance Range | 2200 μF |
| Capacitance Tolerance | ±20% |
| at 20°C, 120Hz | |

2/16/2023



DIP ALUMINUM ELECTROLYTIC CAPACITORS 1T SERIES

Table 2

| ITEM | | CHARACTERISTICS | | | | | | | | |
|-------------------------|--|--|-------------|-------------|-------------|------------|------------|------------|-----------|-----|
| Nominal Capacitance | <condition></condition> | | | | | | | | | |
| (Tolerance) | Measurii | Measuring Frequency : 120Hz±12Hz | | | | | | | | |
| | Measurin | Measuring Voltage : Not more than 0.5Vrms | | | | | | | | |
| | Measurin | ig Temp | perature | : 20±2°C | | | | | | |
| | <criteria< td=""><td colspan="5"><criteria></criteria></td></criteria<> | <criteria></criteria> | | | | | | | | |
| | Shall be v | Shall be within the specified capacitance tolerance | | | | | | | | |
| Leakage Current | <conditio< td=""><td>on></td><td></td><td></td><td></td><td></td><td></td><td></td><td></td><td></td></conditio<> | on> | | | | | | | | |
| | After DC | Voltage | e is applie | ed to capa | citors thro | ough the s | series pro | otective i | resistor | |
| | (1kΩ±100 | ጋ) so th | at termir | nal voltage | e may read | ch the rea | cted use | voltage. | The leaka | ige |
| | current w | hen m | easured i | in 2 minut | es shall n | ot exceed | the valu | es of the | following | 3 |
| | equation | | | | | | | | | |
| | <criteria< td=""><td colspan="5"><criteria></criteria></td></criteria<> | <criteria></criteria> | | | | | | | | |
| | I (μΑ)≤0.0 | I (μΑ)≤0.01CV or 3 (μΑ) whichever is greater. | | | | | | | | |
| | I: Leakage | e currer | nt (µA) | | | | | | | |
| | C: Capaci | C: Capacitance (µF) | | | | | | | | |
| | V: Rated | V: Rated DC working voltage (V) | | | | | | | | |
| tanδ | <conditio< td=""><td colspan="3"><condition></condition></td></conditio<> | <condition></condition> | | | | | | | | |
| | See Nom | See Nominal capacitance, for measuring frequency, voltage and temperature. | | | | | | | | |
| | W.V | ′(V) | 10 | 16 | 25 | 35 | 50 | 63 | 100 | |
| | Tan δ | Max. | 0.20 | 0.16 | 0.14 | 0.12 | 0.10 | 0.09 | 0.08 | |
| | <criteria< td=""><td>></td><td></td><td></td><td></td><td></td><td></td><td></td><td></td><td></td></criteria<> | > | | | | | | | | |
| | For capac | citance | value >10 | 000uF, ad | d 0.02per | another | 1000uF | | | |
| Rated Voltage | | | | | | | | | | |
| (WV)/Surge Voltage (SV) | | WV 6.3 10 16 25 35 50 63 100 | | | | | | | | |
| | SV | 8.0 | 13 | 20 | 32 | 44 | 63 | 79 | 125 | |
| | | | | | | | | | | |
| | | | | | | | | | | |
| | | | | | | | | | | |

2/16/2023



DIP ALUMINUM ELECTROLYTIC CAPACITORS 1T SERIES

| Item | | Characteristics | | | | | | | | |
|--------------------------------------|--|---|-------------|----------|---------|-----------------------------------|---------------------------------------|---------------|----------|--|
| Terminal Strength IEC-60384-4 4.4 | <condition> Tensile streng</condition> | gth of termi | inals Fixe | ed the o | capacit | or, appli | ied for | ce to the ter | minal in | |
| | lead out dired | tion for 10 | \pm 1 sec | onds. B | ending | strengt | h of te | rminals. Fixe | d the | |
| | capacitor, ap | capacitor, applied force to bent the terminal (1 4 mm from the rubber) for 900 | | | | | | | | |
| | within 2~3 se | within 2~3 seconds, and then bent it for 90o to its original position within 2~3s. | | | | | | 1 2~3s. | | |
| | Diam | Diameter of lead wire Tensile force N (kgf) Bending force N | | | | | e N (kgf | | | |
| | 0. | 5mm and le | ess | | 5 (0 | .51) | | 2.5 (0.2 | 25) | |
| | Over | 0.5mm to 0 | .8mm | | 10 (| 1.0) | | 5 (0.51 | L) | |
| | < Criteria> No noticeable | e changes s | hall be f | ound, r | io brea | kage or | loosen | ess at the te | erminal | |
| Temperature | <condition></condition> | | | | | | | | | |
| Characteristics IEC-60384-4 4.12 | Step | Testing | temper | ature(° | C) | | | Time | | |
| | 1 | | 20±2 | | | Time to reach thermal equilibrium | | | | |
| | 2 | (- | (-55) -25±3 | | | Time to reach thermal equilibrium | | | | |
| | 3 | 20±2 | | | | Time to reach thermal equilibrium | | | | |
| | 4 | | 105 ± 2 | | | Time to reach thermal equilibrium | | | | |
| | 5 | | 20±2 | | | Time to reach thermal equilibrium | | | | |
| | capacitance, +105°C shall r within the lim c. At-55°C (-2 | <criteria></criteria> a. At +105°C: capacitance shall be within ±20% of its original value at +20°C measured capacitance, tan δ shall be within the limit of tan δ , The leakage current value at +105°C shall not more than 8 times of its specified value. b. In step 5, tan δ shall be within the limit of tan δ , The leakage current shall not more than the specified value c. At-55°C (-25 °C), Impedance (Z) ratio shall not exceed the value of the following table. d. Capacitance, tan δ , and impedance shall be measured at 120Hz. | | | | | alue at δ shall be ified value. | | | |
| | Rated Vo | ltage (V) | 6.3 | 10 | 16 | 25 | 35 | 50/63 | 100 | |
| | Z-25°C/ Z+20°C | < ФD16 | 4 | 3 | 3 | 2 | 2 | 2 | 2 | |
| | | ≥ Φ16 | 5 | 4 | 3 | 2 | 2 | 2 | 3 | |
| | Z-40°C/ 55°CZ+ | < Ф16 | 8 | 6 | 4 | 4 | 4 | 3 | 3 | |
| | 20°C | ≥Ф16 | 12 | 8 | 6 | 4 | 3 | 3 | 6 | |
| 2/16/2023 | | | | | | | | | | |



DIP ALUMINUM ELECTROLYTIC CAPACITORS 1T SERIES

| ltem | | Characteristics | | | | |
|-------------------------------------|--|--|--|--|--|--|
| Load Life Test IEC-60384-4 4.13 | <condition> According to IEC60384-4 No.4.13 methods, The capacitor is stored at a temperatur of $105 \pm 2^\circ$ C with DC bias voltage plus the rated ripple current for 2000+48/0 hour (The sum of DC and ripple peak voltage shall not exceed the rated working voltage) Then the product should be tested after 16 hours recovering time at atmospheric conditions. The result should meet the following table: Criteria> The characteristic shall meet the following requirements. The specified value shall be satisfied</condition> | | | | | |
| | Capacitance Change tanδ Appearance | Within \pm 20% of initial valueNot more than 200% of the specified value.There shall be no leakage of electrolyte. | | | | |
| Shelf Life Test IEC-60384-4 4.17 | <condition> The capacitors are then stored with no voltage applied at a temperature of 105±2°C for 1000+48/0 hours. Following this period the capacitors shall be removed from the test chamber and be allowed to stabilized at room temperature for 4~8 hours. Next they shall be connected to a series limiting resistor(1k±100Ω) with D.C. rated voltage applied for 30min. After which the capacitors shall be discharged, and then, tested the characteristics. <criteria> The characteristic shall meet the following requirements.</criteria></condition> | | | | | |
| | Leakage currentThe specified value shall be satisfiedCapacitance ChangeWithin ±20% of initial value | | | | | |
| | tanδNot more than 200% of the specified value.AppearanceThere shall be no leakage of electrolyte. | | | | | |
| | | red more than 1 year, the leakage current may rough about 1 K Ω resistor, if necessary. | | | | |

2/16/2023



DIP ALUMINUM ELECTROLYTIC CAPACITORS 1T SERIES

| Item | | Characteristics | | |
|---------------------------------------|---|---|--|--|
| Surge Test IEC-60384-4 4.9 | No. of cycles: 1000cycles Eac "ON" for 30±5 < Criteria> Leakage current Capacitance Change tanδ Appearance |) Test voltage: Surge voltage item 4.4 h cycles lasts for 6 ± 0.5 min s "OFF" for 5 ± 0.5 min Not more than the specified value Within $\pm15\%$ of initial value Not more than the specified value There shall be no leakage of electrolyte. | | |
| | applicable to such over voltage | | | |
| Solderability test IEC-60384-4 4.6 | <condition> The capacitor shall be tested under the following conditions: Soldering temperature : 245±3°C Dipping depth : 2mm Dipping speed : 25±2.5mm/s Dipping time : 3±0.5s <criteria> <criteria> Coating quality : A minimum of 95% of the surface being immersed</criteria></criteria></condition> | | | |



DIP ALUMINUM ELECTROLYTIC CAPACITORS 1T SERIES

| ltem | Characteristics | | | | | | |
|---------------------------|---|--|--|--|--|--|--|
| Vibration Test | <condition></condition> | | | | | | |
| IEC-60384-4 4.8 | The following conditions shall be applied for 2 hours in each 3 mutually | | | | | | |
| | perpendicular directions. | | | | | | |
| | Vibration frequency rang | | | | | | |
| | | Peak to peak amplitude : 1.5mm | | | | | |
| | | z ~ 10Hz in about 1 minute | | | | | |
| | | capacitor with diameter greater than 12.5mm or longer than | | | | | |
| | 25mm must be fixed in p | | | | | | |
| | 4mm or less Within 30° To be soldered | | | | | | |
| | | | | | | | |
| | <criteria></criteria> | | | | | | |
| | After the test, the following items shall be tested: | | | | | | |
| | Inner construction | No intermittent contacts, open or short circuiting. No damage of tab terminals or electrodes | | | | | |
| | Appearance | No mechanical damage in terminal. No leakage of electrolyte or swelling of the case. The markings shall be legible | | | | | |
| Resistance To Solder Heat | | | | | | | |
| Test | <condition></condition> | ar shall be immersed into solder both at | | | | | |
| IEC-60384-4 4.5 | Terminals of the capacitor shall be immersed into solder bath at 260±5°Cfor10±1seconds or 400±10°Cfo for3 01 seconds to 1.5~2.0mm from the | | | | | | |
| | body of capacitor. Then the capacitor shall be left under the normal temperature and | | | | | | |
| | normal humidity for 1~2 hours before measurement. | | | | | | |
| | | | | | | | |
| | <criteria></criteria> | | | | | | |
| | Leakage current | Not more than the specified value | | | | | |
| | Capacitance Chang | ge Within \pm 10% of initial value | | | | | |
| | tanδ | Not more than the specified value | | | | | |
| | | | | | | | |

2/16/2023

10



DIP ALUMINUM ELECTROLYTIC CAPACITORS 1T SERIES

| ltem | Characteristics | | | |
|-------------------------------|---|---|--|--|
| Change Of Temperature Test | <condition> Temperature cycle: According to IEC60384-4 No.4.7 methods, capacitor shall be placed in an oven, the condition according as below:</condition> | | | |
| IEC-60384-4 4.7 | Temperature | Time | | |
| | (1)+20°C | ≤ 3 Minutes | | |
| | (2)-40°C | 30±2 Minutes | | |
| | (3)+105°C | 30±2 Minutes | | |
| | (1) To (3) = 1 cycle, Tota | al 5 Cycles | | |
| | <criteria> The characteristic shall meet the following requirement.</criteria> | | | |
| | Leakage current | Not more than the specified value. | | |
| | Tan δ | Not more than the specified value. | | |
| | Appearance | There shall be no leakage of electrolyte. | | |
| | <criteria> Leakage current Capacitance Change</criteria> | Not more than the specified value.Within $\pm 20\%$ of initial valueNot more than 120% of the specified value. | | |
| | Tan δ | Not more than 120% of the specified value. | | |
| | Appearance | There shall be no leakage of electrolyte. | | |
| Vent Test IEC-60384-4 4.16 | Condition> The following test only apply to those products with vent products at diameter with vent. D.C. test The capacitor is connected with its polarity reversed to a D source. Then a current selected from Table 2 is applied. | | | |
| | Diameter (mm) | DC Current (A) | | |
| | 22.4 or less | 1 | | |
| | Criteria> The vent shall operate with no dangerous conditions such as flames or dispersion of pieces of the capacitor and/or case. | | | |
| 2/16/2023 | | 11 | | |



DIP ALUMINUM ELECTROLYTIC CAPACITORS 1T SERIES

CASE SIZE & MAX RIPPLE CURRENT

| Rated Voltage (V) | Capacitance (Tol.+/-20%) (μF) | Case Size Ø*L (mm) | Tanδ @+105°C, 120Hz | Ripple Current @+105°C, 120Hz (mA r.m.s .) |
|----------------------|-------------------------------------|--------------------------|------------------------|--|
| 25 | 2200 | 13.0*25.0 | 0.14 | 1110 |

FREQUENCY COEFFICIENT OF ALLOWABLE RIPPLE CURRENT

| Cap. | Frequency | 50Hz(60Hz) | 120Hz | 500Hz | 1KHz | ≥10kHz |
|--------|-------------|------------|-------|-------|------|--------|
| 2200µF | Coefficient | 0.80 | 1.0 | 1.1 | 1.12 | 1.15 |

Remark:

1) Specification are subject to change without notice should a safety or technical concern arise regarding the

product ,please be sure to contact our sales offices

2) The sizes in the above table are all general specifications. If you need other specifications, please contact us.

| Ambient Temperature(°C) | 105 | 85 | ≤70 |
|----------------------------|-----|-----|-----|
| Coefficient | 1.0 | 1.5 | 2.0 |

2/16/2023



DIP ALUMINUM ELECTROLYTIC CAPACITORS 1T SERIES

ATTENTION

When using Aluminum Electrolytic Capacitor, please pay attention to the points listed below. If the following types of electrical loads are applied to Aluminum Electrolytic Capacitor, rapid deterioration of electrical property occurs:

- Reverse voltage
- Overvoltage exceeding rated working voltage
- · Current exceeding rated ripple current
- Severe charging/discharging

At such time, severe heat is generated, gas electrolyte leaks from the sealed area, and pressure relief vent operates due to increase of internal pressure. In the worst case, explosion or ignition may occur, and along with destruction of the capacitor combustibles may burst out.

1.CAUTION DURING CIRCUIT DESIGN

1) OPERATIONAL ENCIRONMENT, MOUNTING ENVIRONMENT ANDCONDITIONS Ensure that operational and mounting conditions follow the specified conditions detailed in the catalog and specification sheets

2) OPERATING TEMPERARURE, RIPPLE CURRENT AND LOAD LIFE.

Operating temperature and applied ripple current should be within the specified value in the catalog or specification sheets. Do not use Aluminum Electrolytic Capacitors at temperature which exceeds the specified category temperatures range. Do not apply excessive current to the capacitors, which exceeds the specified rated ripple current. During circuit design ,please ensure that capacitors are selected to match with the lifetime requirements of the application

3) APPLICATION

Aluminum Electrolytic Capacitors are normally polarized .Reverse voltage or AC Voltage should not be applied. When polarity may flip over, non-polar type should be used, but the non-polar type cannot be used for AC. Standard Aluminum Electrolytic Capacitors are not suitable for rapid charge and discharge applications. Group in your area about specialty signed capacitors for rapid charge and discharge.


4) APPLIED COLTAGE

Do not exceed the rated voltage of capacitors

5) INSULATION

Aluminum Electrolytic Capacitors should be electrically isolated from the following. Aluminum case, cathode lead wire, anode lead wire and circuit pattern; Auxiliary terminals of snap-in type, anode terminal, outward terminals and circuit pattern. The PVC sleeve of Aluminum Electrolytic Capacitors is not recognized as an insulator, and therefore ,the standard capacitor should not be used in a place where insulation function is needed. Please consult with Shanghai Suzuki Electronics or sales office of Suzuki Techno Group in your area, if you require a higher grade of insulating sleeve.

2/16/2023



DIP ALUMINUM ELECTROLYTIC CAPACITORS 1T SERIES

6) CONDITIONS OF USE

The following environments should be avoided when suing Aluminum Electrolytic Capacitors. Damp conditions such as water ,salt water or oil spray or fumes, high humidity or humidity condensation situations. Hazardous gas/fumes such as hydrogen sulfide, sulfurous acid gas, nitrous acid, chlorine gas, ammonia or bromine gas; Exposure of ozone ,ultraviolet rays or radiation; Severe vibration or shock which exceeds the condition specified in the catalog or specification sheet.

7) CONSIDERATION TO ASSEMBLY CONDITION

In designing a circuit ,the following matters should be ensured in advance to the capacitor's assembly on the printed circuit board (PC board) Design the appropriate hole spacing to match the lead pitch of capacitors; Do not locate any wiring and circuit patterns directly above the capacitor's vent; Ensure enough free space above the capacitor's vent. The recommended space is specified in the catalog or specification sheets; In case the capacitor's vent is facing the PC board, make a gas release hole on PC board. The sealing side of the screw terminal type should not face down in the application. When the capacitors are mounted horizontally, the anode screw terminals must be positioned at upper side..

8) CONSIDERATION TO CIRCUIT DESIGN

Any copper lines or circuit patterns should not be laid under the capacitor; Parts which radiate heat should not be placed close to the reverse side of the Aluminum Electrolytic Capacitors on the PC board.

9) OTHERS

Performance of electrical characteristics of Aluminum Electrolytic Capacitors is affected by variation of operating temperature and frequency. Consider this variation when designing the circuit. Excessive holes and connection hole between both sides on the PC board should be avoided around or under the mounting area of the Aluminum Electrolytic Capacitors on double sided or multilayer PC board. Torque of tightening screw terminals should not exceed the specified maximum value which is described in the catalog and specification sheets . Consider current balance when 2 or more Aluminum Electrolytic Capacitors are connected in parallel. Use bleeding resistors when 2 or more Aluminum Electrolytic Capacitors are connected in series .In this case, the resistors should be connected parallel to the capacitors.

2. CAUTION FOR ASSEMBLING CAPACITORS

1) CAUTION BEFORE ASSEMBLY

Aluminum Electrolytic Capacitors cannot be recycled after mounting and applying electricity in unit. The capacitors, which are removed from PC board for the purpose of measuring electrical characteristics at the periodical inspection, should only be recycled for the same position.; Aluminum Electrolytic Capacitors may accumulate charge naturally during storage. In this case, discharge through a 1KOHM resistor before use; Leakage current of Aluminum Electrolytic Capacitors may be increased during long storage time. In this case, the capacitors should be subject to voltage treatment through a 1KOHM resistor before use.

2/16/2023



DIP ALUMINUM ELECTROLYTIC CAPACITORS 1T SERIES

2) IN THE ASSEMBLY PROCESS-1

Ensure rated voltage and capacitance of the capacitors before mounting; Ensure capacitors polarity before mounting; Do not use a capacitor which has been dropped onto a hard surface; Do not use a capacitor with damaged or dented cased or seals.

3) IN THE ASSEMBLY PROCESS-2

Capacitors should be mounted after confirmation that hole spacing on PC board matches the lead pitch of the capacitors; The snap-in type of capacitors should be mounted firmly on the PC board without a gap between the capacitor body and the surface of PC board;. Avoid excessive force when clinching lead wire during auto-insertion process; Avoid excessive shock to capacitors by automatic inserting machine, during mounting, parts inspection or centering operations; Please utilize supporting material such as strap of adhesive to mount capacitors to PC board when it is anticipated that vibration or shock is applied.

4) SOLDERING

Soldering conditions (temperature and time)should be within the specified conditions which are described in the catalog or specification sheets; In case lead wire reforming is needed due to inappropriate pitch between capacitor and holes on PC board, stress to the capacitor should be avoided; In case of maintenance by soldering iron, if it is required to detach the capacitor, it should be removed from PC board after solder has melted sufficiently in order to reduce stress on the lead wires/terminals of the capacitor; Soldering iron should never touch the capacitor's body.

5) FLOW SOLDERING

Do not dip capacitor's body into melted solder. It should only be soldered on the reverse side of the PC board on which the capacitors are mounted; Soldering condition (preheat, soldering temperature, dipping time)should be within the specified standard which is described in the catalog or specification sheets; Flux should not be adhered to capacitor's body but only to its terminals; Other devices which are mounted close to capacitors should not touch the capacitors.

6) REFLOW SOLDERING

Reflow soldering conditions(preheat, soldering, temperature, reflow time)should follow the specified standard which is described in the catalog or specification sheets; Heating standard should depend on surface of the capacitor color or materials when infrared rays are used because the capacitor's heat absorption depends on the surface color or materials. Check heat condition; Standard Aluminum Electrolytic Capacitors cannot withstand two or more reflow processes.

7) HANDLING AFTER SOLDERING Do not bend or twist the capacitor's body after soldering on PC board; Do not pick-up or move PC board by holding the soldered capacitors; Do not hit the capacitors and isolate capacitors from the PC board or other device when stacking PC boards in store.

2/16/2023



DIP ALUMINUM ELECTROLYTIC CAPACITORS 1T SERIES

8) PC BOARD CLEANING

Standard Aluminum Electrolytic Capacitors should be free from halogenated solvents during PC board cleaning after soldering

9) ADHESIVES AND COATNG MATERIALS

Do not use halogenated adhesives and coating materials to fix Aluminum Electrolytic Capacitors; Flux between the surface of the PC board and sealing of capacitors should be cleaned before using adhesives or coating materials; Solvents should be dried up before using adhesives or coating materials; Do not cover up all the sealing area of capacitors with adhesives or coating materials, make coverage only partial.

3. CAUTION DURING USE OF CAPACITORS IN SETS

1) Do not touch the terminals of capacitors;

2) Do not connect electrical terminals of the capacitors. Keep the capacitors free from conductive solution, such as acid, alkali and so on;

3) Ensure the operational environment of the equipment in which the capacitor has been built is within the specified condition mentioned in the catalog or specification sheets.

4. MAINTENANCE

1) Periodical inspection should be carried out for the capacitors, which are used with industrial equipment;.Check the following points at the inspection.

2) Visual inspection to check pressure relief vent open or leakage of electrolyte.

3) Electrical characteristics: leakage current, capacitance, dissipation factor and the other points which are mentioned in the catalog or specification sheets.

5. EMERGENCY ACTION

1) If the pressure relief vent is open and some gas blows out from the capacitor, turn the main switch of the equipment off or pull out the plug from the power outlet immediately.

2) During pressure relief vent operation, extremely hot gas (over 100°C)may blow out from the vent area of the capacitors. So keep your face and skin away from capacitors during its operation. In case of eye contact, flush the open eye(s)with large amount of clean water immediately. In case of ingestion, gargle with water immediately, and do not swallow .Also do not touch electrolyte but wash skin with soap and water in case of skin contact.

6. STORAGE CONDITIO

1) Aluminum Electrolytic Capacitors should not be stored in high temperature or in high humidity. The suitable storage condition is 5°C-35°C, and less than 75% in relative humidity;

2) Aluminum Electrolytic Capacitors should not be stored in damp conditions such as water, salt water spray or oil spray;

3) Do not store Aluminum Electrolytic Capacitors in an environment full of hazardous gas (hydrogen sulfide gas, sulfurous acid gas, nitrous acid, chlorine gas, ammonia or bromine gas.

2/16/2023



DIP ALUMINUM ELECTROLYTIC CAPACITORS 1T SERIES

4) Aluminum Electrolytic Capacitors should not be stored under exposure to ozone ,ultraviolet rays or radiation.

5) After one year, a capacitor should be reconditioned by applying rated voltage in series with a 1000Ω current limiting resistor for a time period of 30 minutes .

7. DISPOSAL

1) Please take either of the following actions in case of disposal. Incineration (high temperature of more than 800°C) after crushing the capacitor's body; Consignment to specialists of industrial waste.

DISCLAIMER

NextGen Component, Inc. reserves the right to make changes to the product(s) and or information contained herein without notice. No liability is assumed as a result of their use or application. No rights under any patent accompany the sale of any such product(s) or information

2/16/2023