# SUNON

# SPECIFICATION FOR APPROVAL


CUSTOMER	:
DESCRIPTION	: DC BRUSHLESS Fan
DIMENSIONS	: 84X80.9X7.5 mm
MODEL	: EG75050S1-C031-S9A
SUNON SPEC. NO.	: D07026140F-00
CUSTOMER APPROVAL NO.	:
REVISION	:
APPROVED BY CUSTOMER (AUTHORIZED)	:

DRAWN Nancy 01/16 CHECK					SPEC.NO	D07026140F-00	
	•	CHECKED	Dolphin	APPROVED	Dolphin	<b>ISSUE DATE</b>	01. 16. 2020
						EDITION	0
						<b>REVISION DATI</b>	E
						E.SPEC	E11900560
建準電板	幾工業股份很	有限公司					
SUNONWEALTH ELECTRIC MACHINE INDUSTRY CO., LTD.							
NO. 30,	LN. 296, XI	NYA RD.	, QIANZHEN	NDIST.,	TEL:886	-7-8135888	
KAOHS	SIUNG CIT	Y 80673, T	TAIWAN (R.C	<b>D.C</b> )	FAX:886	-7-8230505/82306	606/8231010
URL:http://www.sunon.com E-mail: sunon@email.sunon.com.tw						on.com.tw	

建準電機 SUNONWEALTH Page 1 of 17



# I. MODEL NUMBERING SYSTEM





# **II. SPECIFICATION**

# **1. MECHANICAL CHARACTERISTIC**

MOTOR DESIGN	3 phase, 4-poles Brushless DC motor
BEARING SYSTEM	Lubricated Sleeve Bearing System
DIMENSIONS	See Page 6
MATERIALS OF COVER	SECC+Thermoplastic PBT of UL 94V-0
MATERIALS OF HOUSING	SUS304 1/2H
MATERIALS OF FAN BLADE	Thermoplastic LCP of UL 94V-0
DIRECTION OF ROTATION	Counter-clockwise viewed from front of fan blade
MOUNTING HOLES	Diameter 1.6 mm in 1 hole
WEIGHT	44 g

# 2. ELECTRIC CHARACTERISTIC

RATED VOLTAGE	5 VDC
RATED CURRENT	270 mA / Max. 297 mA
RATED POWER CONSUMPTION	1.35 WATTS / MAX. 1.49 WATTS
SAFETY POWER CONSUMPTION	2.25 WATTS
OPERATING VOLTAGE RANGE	2.5~5 VDC
STARTING VOLTAGE	2.5 VDC (25 deg. C POWER ON/OFF)
OPERATING TEMPERATURE RANGE	-10 to + 70 deg. C
STORAGE TEMPERATURE RANGE	-40 to + 70 deg. C



建準電機 SUNONWEALTH Page 3 of 17

# **3. PERFORMANCE CHARACTERISTIC**


RATED SPEED	4000 RPM ± 7% at rated voltage
AIR FLOW	4.4 CFM / Min. 4.0 CFM
STATIC PRESSURE	0.51 Inch-H <sub>2</sub> O /MIN. 0.40 Inch-H <sub>2</sub> O
ACOUSTIC NOISE	35.9 dB(A) / MAX. 38.7 @ 0.5M
	29.9 dB(A) / MAX. 32.7 @ 1M
AIR FLOW V.S. PRESSURE	See Page 5
INSULATION CLASS	UL Class A
INSULATION RESISTANCE PLASTIC HOUSING	10M ohm at 500 VDC between internal stator and lead wire (+)
DIELECTRIC STRENGTH	Applied AC 500 V for one minute or AC 600 V for 2 Seconds between housing and lead wire (+)
LIFE EXPECTANCY	35,000 Hours at 40 deg. C, 65% humidity, 90% CL.
PROTECTION	Automatic Restart Note: The motor will shut down when rotor was locked, then auto restart within 10 seconds.
	□Polarity Protection

# 4. SAFETY

SAFETY	UL	CUR	TUV	CE
NO.	E77551	E77551	$\checkmark$	$\checkmark$




建準電機 SUNONWEALTH Page 4 of 17






建準電機 SUNONWEALTH Page 5 of 17














建準電機 SUNONWEALTH Page 7 of 17

# FAN 3<sup>rd</sup> WIRE SIGNAL

# F Type (Frequency Generator)








★Electrical Characteristics : (at Ta =  $25^{\circ}$ C) Vcc =  $5V\pm10\%$ 

Dar	ameter		Ratings		Unit
1 410	ameter	min	typ.	max	Om
FG Supply	Voltage(V+)	2.4	V+	Vec	Voltage
FG Outpu	t Current (If)			10	mA
FG Ou	tput (VL)			0.4	Voltage
FG Ou	tput (VH)		V+		Voltage
Ratio	(=t1/t2)		2.45		
FG Output Voltage		T2	T3		VL
	-	T = 1	Rotation		
	T⁼	$= T1 + T2 + T$ $T = - \frac{1}{1}$	Γ3+T4=1 I 60 rpm	Rotation	

建準電機 SUNONWEALTH Page 8 of 17



# **PWM INPUT SIGNAL**



**2. Duty Cycle (D.C.)**  $\frac{t1}{t1+t2}$ \*100= $\frac{t1}{T}$ \*100(%).

#### 3.PWM Duty Cycle VS Speed (at Ta = 25°C, Vcc =5V, fpwm=23KHz

PWM Duty Cycle (%)	FAN Speed ( R.P.M.) (REF.)
28	1750±30%
100	4000±7 <b>%</b>

★Electrical Characteristics : ( at Ta =  $25^{\circ}$  · Vcc = 5V.)

Parameter	Min	Typical	Max	Unit
f pwm	20K	23K	50K	Hz
V <sub>H</sub>	2.5	-	5	V
V <sub>L</sub>	0	-	1	V
Isource	0	-	5	mA
D.C.	28	-	100	%

\* The speed is default to be maximum if PWM input pin is unconnected.


\* Min. start up duty cycle is 28%. Please don't apply 1 ~ 27% duty cycle to prevent unstable fan speed.



### **FOR REFERENCE**

# **DUTY CYCLE & SPEED CURVE**

■ Duty Cycle v.s. Speed curve @ Vcc= rated volt.							
PWM控制頻率: 23K Hz							
28%	40%	50%	60%	70%	80%	90%	100%
1750	2400	2800	3100	3400	3600	3800	4000
	28%	23K 28% 40%	23K Hz 28% 40% 50%	23K Hz 28% 40% 50% 60%	<u>23K Hz</u> <b>28% 40% 50% 60% 70%</b>	23K Hz 28% 40% 50% 60% 70% 80%	23K Hz 28% 40% 50% 60% 70% 80% 90%





# **III. OTHER SPECIFIED TESTING**

The following is a general description of certain tests that are performed on representative SUNON fans. Nothing in this document is intended to suggest that these tests are performed on every model of SUNON fan. Moreover, the descriptions that follow each test are meant only to provide a general explanation of each test. If you would like a more detailed explanation as to any test identified in this Section, SUNON can provide such an explanation upon request.

#### 1. DROP PROOF TEST

Fans are packaged in a standard size shipping box and are dropped to the ground from certain heights and angles depending on the weight of the particular box.

#### 2. HUMIDITY PROOF TEST

The fan is operated for 96 continuous hours in an environment with humidity of 90% to 95% RH at  $60^{\circ}C \pm 2^{\circ}C$ .

### 3. VIBRATION PROOF TEST

Vibration with an amplitude 2mm and a frequency of 5-55-5hz is applied in all 3 directions (X,Y,Z), in cycles of 1 hour each, for a total vibration time of 3hours.

## 4. THERMAL CYCLING TEST

The fan is operated in a testing chamber for 50 cycles. In each cycle, the temperature is gradually increased from -10°C to 70°C for 90 minutes, and subsequently operated at 70°C for 120 minutes. The temperature is then gradually decreased from 70°C to -10°C for 90 minutes, and subsequently operated at -10°C for 120 minutes.

## 5. SHOCK PROOF TEST

100G of force is applied in the 3 directions (X,Y, and Z) for 2 milliseconds each.

## 6. LIFE EXPECTANCY

The "Life Expectancy" of SUNON fans is determined in SUNON's reliability test laboratory by using temperature chambers. The "Life Expectancy" of this fan has not been evaluated for use in combination with any end application. Therefore, the Life Expectancy Test Reports (L10 and MTTF Report) that relate to this fan are only for reference.




建準電機 SUNONWEALTH Page 11 of 17

# **IV. CHARACTERISTIC DEFINITION**

The following is a general description of certain tests that are performed on representative SUNON fans in order to determine the specifications of the fan. Nothing in this document is intended to suggest that these tests are performed on every model of SUNON fan. Moreover, the descriptions that follow each test are meant only to provide a general explanation of each test. If you would like a more detailed explanation as to any test identified in this Section, SUNON can provide such an explanation upon request.

#### **1. ACOUSTICAL NOISE**

Measured in a semi-anechoic chamber with background noise level below 15dB(A).



1 METER FROM MICROPHONE TO FAN INTAKE

The fan is running in free air under shaft horizontal condition with the microphone at distance of one meter from the fan intake.

#### **2. INPUT POWER**

Measured after continuous 10 minute operation at rated voltage in clean air (STATIC PRESSURE=0), and at ambient temperature of 25 degrees C under shaft horizontal condition.

#### **3. RATED CURRENT**

Measured after continuous 10 minute operation at rated voltage in clean air (STATIC PRESSURE=0), and at ambient temperature of 25 degrees C under shaft horizontal condition.



建準電機 SUNONWEALTH Page 12 of 17

#### 4. RATED SPEED

Measured after continuous 10 minute operation at rated voltage in clean air (STATIC PRESSURE=0), and at ambient temperature of 25 degrees C under shaft horizontal condition.

#### **5. STARTING VOLTAGE**

Measured the voltage which enables to start the fan in the clean air (static pressure = 0) by switching on at the voltage under shaft horizontal condition. It is not at continuously increasing voltage adjustment.

#### 6. LOCKED ROTOR CURRENT

Measured immediately after the fan blade is locked.

#### 7. AIR FLOW AND STATIC PRESSURE

The performance specification of air flow and static pressure shown in this specification for approval is measured using the exhaust method. A double chamber is used in accordance with AMCA 210 standard or DIN 24163 specification . The values are recorded when the fan speed has stabilized at rated voltage.

#### 8. INSULATION RESISTANCE

- 1. PLASTIC HOUSING:
  - (1) Measured between internal stator and lead wire(+).
  - (2) Measured between housing and lead wire(+).

#### 2. ALUMINIUM HOUSING:

Measured between internal stator and lead wire(+).

#### 9. DIELECTRIC STRENGTH

Measure between housing and lead wire(+).



建準電機 SUNONWEALTH Page 13 of 17

# V. NOTE

# **I**.SAFETY

- 1. DO NOT use or operate this fan in excess of the limitations set forth in this specification. SUNON is not responsible for the non-performance of this fan and/or any damages resulting from its use, if it is not used or operated in accordance with the specifications.
- 2. SUNON recommends adding a protection circuit to the product or application in which this fan is installed, such as a thermo-fuse, or current-fuse or thermo-protector. The failure to use such a device may result in smoke, fire, electric shock by insulation degradation in cases of motor lead short circuit, overload, or over voltage, and/or other failure.
- 3. SUNON recommends installing a protection device to the product or application in which this fan is installed if there is a possibility of reverse-connection between VDC (+) and GND (-). The failure to install such a device may result in smoke, fire, and/or destruction, although these conditions may not manifest immediately.
- 4. This fan must be installed and used in compliance with all applicable safety standards and regulations.
- 5. Use proper care when handling and/or installing this fan. Improper handling or installation of this fan may cause damage that could result in unsafe conditions.
- 6. Use proper care during installation and/or wiring. Failure to use proper care may cause damage to certain components of the fan including, but not limited to, the coil and lead wires, which could result in smoke and/or fire.
- 7. DO NOT use power or ground PWM to control the fan speed. If the fan speed needs to be adjusted, please contact SUNON to customize the product design for your application.
- 8. For critical or extreme environments, including non stop operation, please contact SUNON and we will gladly provide assistance with your product selection to ensure an appropriate cooling product for your application.



建準電機 SUNONWEALTH Page 14 of 17

# **II. SPECIFICATION MODIFICATION**

- 1. SUNON offers engineering assistance on fan installation and cooling system design.
- 2. All changes, modifications and/or revisions to the specifications, if any, are incorporated in the attached specifications.
- 3. No changes, modifications and/or revisions to these specifications are effective absent agreement, by both SUNON and the customer, in writing.
- 4. This fan will be shipped in accordance with the attached specification unless SUNON and the customer have agreed otherwise, in writing, as specified in Paragraph 3, above.

# **III. OTHER**

- 1. When building your device, please examine thoroughly any variation of EMC, temperature rise, life data, quality, etc. of this product by shock/drop/vibration testing, etc. If there are any problems or accidents in connection with this product, it should be mutually discussed and examined.
- 2. Use proper care when handling this fan. Components such as fan holders or bearings may be damaged, if touched with fingers or other objects. Additionally, static electricity (ESD) may damage the internal circuits of the fan.
- 3. DO NOT operate this fan in proximity to hazardous materials such as organic silicon, cyanogens, formalin, phenol, or corrosive gas environments including, but not limited to, H<sub>2</sub>S, SO<sub>2</sub>, NO<sub>2</sub>, or Cl<sub>2</sub>.
- 4. SUNON recommends that you protect this fan from exposure to outside elements such as dust, condensation, humidity or insects. Exposure of this fan to outside elements such as dust, condensation, humidity or insects may affect its performance and may cause safety hazards. SUNON does not warrant against damage to the product caused by outside elements.

Re: The term can be excluded, if the fan has been with IP design and meets customer's IP requirement.



建準電機 SUNONWEALTH Page 15 of 17

- 5. This fan must be installed properly and securely. Improper mounting may cause harsh resonance, vibration, and noise.
- 6. Fan guards may prevent injury during handling or installation of the fan and are available for sale with this fan.
- 7. Unless otherwise noted, all testing of this fan is conducted at 25°C ambient temperature and sixty-five percent (65%) relative humidity.
- 8. DO NOT store this fan in an environment with high humidity. This fan must be stored in accordance with the attached specifications regarding storage temperature. If this fan is stored for more than 6 months, SUNON recommends functional testing before using.
- SUNON reserves the right to use components from multiple sources at its discretion. The use of components from other sources will not affect the specifications as described herein.
- 10. The "Life Expectancy" of this fan has not been evaluated for use in combination with any end application. Therefore, the Life Expectancy Test Reports (L10 and MTTF Report) that relate to this fan are only for reference.

#### VI. WARRANTY

This fan is warranted against all defects which are proved to be fault in our workmanship and material for one year from the date of our delivery. The sole responsibility under the warranty shall be limited to the repair of the fan or the replacement thereof, at SUNON's sole discretion. SUNON will not be responsible for the failures of its fans due to improper handing, misuse or the failure to follow specifications or instructions for use. In the event of warranty claim, the customer shall immediately notify SUNON for verification. SUNON will not be responsible for any consequential damage to the customer's equipment as a result of any fans proven to be defective.



建準電機 SUNONWEALTH Page 16 of 17

# **Declaration of Restricted Materials**

Control declaration of environment- related substances/ materials

1. In accordance with the Restriction of Hazardous Substances (RoHS) Directive 2011/65/EU and specific market requirements, Sunon Halogen-Free Product have complied with law and discipline not to employ the forbidden substances, and restrict the allowable concentration of some limited substances deliberately in our components.

No	Substance	Criteria	
1	CFCs & HCFCs (ozone de	epleting substances)	Forbidden
2	<b>Chlorinated Organic Solv</b>	Forbidden	
		Plastic (Frame, Impeller, wire harness, etc.)	<100ppm
		Solder	<1000ppm
3	Lead and its compounds	Steel alloy	<3500ppm
		Aluminium alloy	<4000ppm
		Copper alloy	<4wt%
	Cadmium and its	Solder Parts composed of metals containing zinc	<20ppm
4	compounds	(e.g. brass, zinc for die casting)	<100ppm
	compounds	Plastic	<5ppm
5	PBBs and PBDEs	1 Iustic	Forbidden
6	PCB and PCT		Forbidden
7	CP, Short-chain Chlorina	ted paraffins C10-13, Cl≥48 wt%	Forbidden
8	Mirex		Forbidden
9	PCN		Forbidden
10	Hexavalent Chromium co	mpounds	<100ppm
11	Mercury and its compoun	Forbidden	
12	Asbestos	Forbidden	
13	Organic Tin compounds	Forbidden	
14	Azo compounds	Forbidden	
15	TBBP-A in external case	<1000ppm	
16	Nickel in external case par	<1000ppm	
17	Hexabromocyclododecane	(HBCDD)	<1000ppm
18	Di-butyl Phthalate (DBP)		<1000ppm
19	Benzyl butyl Phthalate (BE		<1000ppm
20	Di-ethylhexyl Phthalate (D	,	<1000ppm
21	Di-isobutyl Phthalate (DIB	P)	<1000ppm
		lame retardants (other than PBBs or PBDEs),	Br<900ppm
22	applicatable item: frame,	bobbin, impeller, lear wire, connector, mylar	Cl<900ppm
	insulator.	Br+Cl<1500ppm	
23	PAHs and its 16 compour	ds in unusual contact material	BaP < 20ppm
	11115 und its 10 compoun		Total <200ppm
	PCB and electroplating m	aterial, PFOS content complianced with	PFOS <u>&lt;</u> 1000ppm;
24	2006/122/EC	according 11.00 content compliancea with	coating material
			$PFOS \le 1 \mu g/m^2$

