

THIS SPEC IS OBSOLETE

Spec No: 001-65282

Spec Title: CY14C256Q/CY14B256Q/CY14E256Q, 256-KBIT

(32K X 8) SPI NVSRAM

Replaced by: NONE



256-Kbit (32K × 8) SPI nvSRAM

Features

- 256-Kbit nonvolatile static random access memory (nvSRAM) internally organized as 32K × 8
 - □ STORE to QuantumTrap nonvolatile elements initiated automatically on power-down (AutoStore) or by using SPI instruction (Software STORE) or HSB pin (Hardware STORE)
 - □ RECALL to SRAM initiated on power-up (Power-Up RECALL) or by SPI instruction (Software RECALL)
 - □ Support automatic STORE on power-down with a small capacitor (except for CY14X256Q1A)
- High reliability
 - ☐ Infinite read, write, and RECALL cycles
 - ☐ 1million STORE cycles to QuantumTrap
 - □ Data retention: 20 years at 85 °C
- 40 MHz and 104 MHz High speed serial peripheral interface (SPI)
- □ 40 MHz clock rate SPI write and read with zero cycle delay
- 104 MHz clock rate SPI write and SPI read (with special fast) read instructions)
- □ Supports SPI mode 0 (0,0) and mode 3 (1,1)
- SPI access to special functions
 - □ Nonvolatile STORE/RECALL
 - □ 8-byte serial number
 - Manufacturer ID and Product ID
 - □ Sleep mode
- Write protection
 - ☐ Hardware protection using Write Protect (WP) pin
 - ☐ Software protection using Write Disable instruction
 - □ Software block protection for 1/4, 1/2, or entire array
- Low power consumption
 - □ Average active current of 3 mA at 40 MHz operation
 - Average standby mode current of 150 μA
 - ☐ Sleep mode current of 8 μA

- Industry standard configurations
 - Operating voltages:
 - CY14C256Q: V_{CC} = 2.4 V to 2.6 V

 - CY14B256Q: V_{CC} = 2.7 V to 3.6 V
 CY14E256Q: V_{CC} = 4.5 V to 5.5 V
 - □ Industrial temperature
 - □ 8- and 16-pin small outline integrated circuit (SOIC) package
 - □ Restriction of hazardous substances (RoHS) compliant


Functional Description

The Cypress CY14X256Q combines a 256-Kbit nvSRAM^[1] with a nonvolatile element in each memory cell with serial SPI interface. The memory is organized as 32K words of 8 bits each. embedded nonvolatile elements incorporate QuantumTrap technology, creating the world's most reliable nonvolatile memory. The SRAM provides infinite read and write cycles, while the QuantumTrap cells provide highly reliable nonvolatile storage of data. Data transfers from SRAM to the nonvolatile elements (STORE operation) takes place automatically at power-down (except for CY14X256Q1A). On power-up, data is restored to the SRAM from the nonvolatile memory (RECALL operation). You can also initiate the STORE and RECALL operations through SPI instruction.

For a complete list of related documentation, click here.

Configuration

Feature	CY14X256Q1A	CY14X256Q2A	CY14X256Q3A
AutoStore	No	Yes	Yes
Software STORE	Yes	Yes	Yes
Hardware STORE	No	No	Yes



1. This device will be referred to as nvSRAM throughout the document.



Contents


Pinouts	3
Pin Definitions	
Device Operation	
SRAM Write	
SRAM Read	
STORE Operation	
AutoStore Operation	
Software STORE Operation	
Hardware STORE and HSB pin Operation	
RECALL Operation	
Hardware RECALL (Power-Up)	
Software RECALL	
Disabling and Enabling AutoStore	
Serial Peripheral Interface	6
SPI Overview	
SPI Modes	
SPI Operating Features	
Power-Up	
Power-Down	
Active Power and Standby Power Modes	
SPI Functional Description	
Status Register	10
Fast Read Status Register	10
(FAST RDSR) Instruction	10
Write Status Register (WRSR) Instruction	
Write Protection and Block Protection	
Write Enable (WREN) Instruction	
Write Disable (WRDI) Instruction	
Block Protection	
Hardware Write Protection (WP)	
Memory Access	
Read Sequence (READ) Instruction	
Fast Read Sequence (FAST_READ) Instruction .	
Write Sequence (WRITE) Instruction	
nvSRAM Special Instructions	
Software STORE (STORE) Instruction	
Software RECALL (RECALL) Instruction	
AutoStore Enable (ASENB) Instruction	15
AutoStore Disable (ASDISB) Instruction	15

Special Instructions	. 16
SLEEP Instruction	. 16
Serial Number	
WRSN (Serial Number Write) Instruction	. 16
RDSN (Serial Number Read) Instruction	. 17
FAST_RDSN	
(Fast Serial Number Read) Instruction	. 17
Device ID	
RDID (Device ID Read) Instruction	. 18
FAST_RDID (Fast Device ID Read) Instruction	. 19
HOLD Pin Operation	. 19
Maximum Ratings	. 20
Operating Range	. 20
DC Electrical Characteristics	
Data Retention and Endurance	. 21
Capacitance	
Thermal Resistance	
AC Test Loads and Waveforms	. 22
AC Test Conditions	
AC Switching Characteristics	. 23
Switching Waveforms	. 24
AutoStore or Power-Up RECALL	. 25
Switching Waveforms	. 25
Software Controlled STORE and RECALL Cycles	. 26
Switching Waveforms	. 26
Hardware STORE Cycle	. 27
Switching Waveforms	. 27
Ordering Information	. 28
Ordering Code Definitions	. 28
Package Diagrams	
Acronyms	. 31
Document Conventions	. 31
Units of Measure	. 31
Document History Page	. 32
Sales, Solutions, and Legal Information	. 34
Worldwide Sales and Design Support	. 34
Products	
PSoC® Solutions	
Cypress Developer Community	
Technical Support	3/



Pinouts

Figure 1. 8-pin SOIC pinout [2, 3, 4]



V_{SS}□8

Pin Definitions

Pin Name [2, 3, 4]	I/O Type	Description
<u>CS</u>	Input	Chip Select. Activates the device when pulled LOW. Driving this pin high puts the device in low power standby mode.
SCK	Input	Serial Clock. Runs at speeds up to a maximum of f _{SCK} . Serial input is latched at the rising edge of this clock. Serial output is driven at the falling edge of the clock.
SI	Input	Serial Input. Pin for input of all SPI instructions and data.
SO	Output	Serial Output. Pin for output of data through SPI.
WP	Input	Write Protect. Implements hardware write protection in SPI.
HOLD	Input	HOLD Pin. Suspends serial operation.
HSB	Input/Output	Hardware STORE Busy: Output: Indicates busy status of nvSRAM when LOW. After each Hardware and Software STORE operation HSB is driven HIGH for a short time (t _{HHHD}) with standard output high current and then a weak internal pull-up resistor keeps this pin HIGH (External pull-up resistor connection optional). Input: Hardware STORE implemented by pulling this pin LOW externally.
V _{CAP}	Power supply	AutoStore Capacitor. Supplies power to the nvSRAM during power loss to STORE data from the SRAM to nonvolatile elements. If AutoStore is not needed, this pin must be left as No Connect. It must never be connected to ground.
NC	No connect	No Connect: This pin is not connected to the die.
V _{SS}	Power supply	Ground
V _{CC}	Power supply	Power supply

HSB

- Notes
 2. HSB pin is not available in 8-pin SOIC packages (CY14X256Q1A/CY14X256Q2A).
 3. CY14X256Q1A part does not have V_{CAP} pin and does not support AutoStore.
 4. CY14X256Q2A part does not have WP pin.



Device Operation

CY14X256Q is a 256-Kbit serial (SPI) nvSRAM memory with a nonvolatile element in each memory cell. All the reads and writes to nvSRAM happen to the SRAM, which gives nvSRAM the unique capability to handle infinite writes to the memory. The data in SRAM is secured by a STORE sequence which transfers the data in parallel to the nonvolatile QuantumTrap cells. A small capacitor (V_{CAP}) is used to AutoStore the SRAM data in nonvolatile cells when power goes down providing power-down data security. The QuantumTrap nonvolatile elements built in the reliable SONOS technology make nvSRAM the ideal choice for secure data storage.

The 256-Kbit memory array is organized as 32K words × 8 bits. The memory can be accessed through a standard SPI interface that enables very high clock speeds up to 40 MHz with zero cycle delay read and write cycles. This nvSRAM chip also supports 104 MHz SPI access speed with a special instruction for read operation. This device supports SPI modes 0 and 3 (CPOL, CPHA = 0, 0 and 1, 1) and operates as SPI slave. The device is enabled using the Chip Select (CS) pin and accessed through Serial Input (SI), Serial Output (SO), and Serial Clock (SCK) pins.

This device provides the feature for hardware and software write protection through the WP pin and WRDI instruction respectively along with mechanisms for block write protection (1/4, 1/2, or full array) using BP0 and BP1 pins in the Status Register. Further, the HOLD pin is used to suspend any serial communication without resetting the serial sequence.

CY14X256Q uses the standard SPI opcodes for memory access. In addition to the general SPI instructions for read and write, it provides four special instructions that allow access to four nvSRAM specific functions: STORE, RECALL, AutoStore Disable (ASDISB), and AutoStore Enable (ASENB).

The major benefit of nvSRAM over serial EEPROMs is that all reads and writes to nvSRAM are performed at the speed of SPI bus with zero cycle delay. Therefore, no wait time is required after any of the memory accesses. The STORE and RECALL operations need finite time to complete and all memory accesses are inhibited during this time. While a STORE or RECALL operation is in progress, the busy status of the device is indicated by the Hardware STORE Busy (HSB) pin and also reflected on the RDY bit of the Status Register.

The device is available in three different pin configurations that enable you to choose a part which fits in best in their application.

The feature summary is given in Table 1.

Table 1. Feature Summary

Feature	CY14X256Q1A	CY14X256Q2A	CY14X256Q3A
WP	Yes	No	Yes
V_{CAP}	No	Yes	Yes
HSB	No	No	Yes
AutoStore	No	Yes	Yes
Power-Up RECALL	Yes	Yes	Yes
Hardware STORE	No	No	Yes
Software STORE	Yes	Yes	Yes

SRAM Write

All writes to nvSRAM are carried out on the SRAM and do not use up any endurance cycles of the nonvolatile memory. This allows you to perform infinite write operations. A write cycle is performed through the WRITE instruction. The WRITE instruction is issued through the SI pin of the nvSRAM and consists of the WRITE opcode, two bytes of address, and one byte of data. Write to nvSRAM is done at SPI bus speed with zero cycle delay.

The device allows burst mode writes to be performed through SPI. This enables write operations on consecutive addresses without issuing a new WRITE instruction. When the last address in memory is reached in burst mode, the address rolls over to 0x0000 and the device continues to write.

The SPI write cycle sequence is defined explicitly in the Memory Access section of SPI Protocol Description.

SRAM Read

A read cycle is performed at the SPI bus speed. The data is read out with zero cycle delay after the READ instruction is executed. READ instruction can be used upto 40 MHz clock speed. The READ instruction is issued through the SI pin of the nvSRAM and consists of the READ opcode and two bytes of address. The data is read out on the SO pin.

A speed higher than 40 MHz (up to 104 MHz) requires FAST_READ instruction. The FAST_READ instruction is issued through the SI pin of the nvSRAM and consists of the FAST_READ opcode, two bytes of address, and one dummy byte. The data is read out on the SO pin.

This device allows burst mode reads to be performed through SPI. This enables reads on consecutive addresses without issuing a new READ instruction. When the last address in memory is reached in burst mode read, the address rolls over to 0x0000 and the device continues to read.

The SPI read cycle sequence is defined explicitly in the Memory Access section of SPI Protocol Description.

STORE Operation

STORE operation transfers the data from the SRAM to the nonvolatile QuantumTrap cells. The device STOREs data to the nonvolatile cells using one of the three STORE operations: AutoStore, activated on device power-down; Software STORE, activated by a STORE instruction; and Hardware STORE, activated by the HSB. During the STORE cycle, an erase of the previous nonvolatile data is first performed, followed by a program of the nonvolatile elements. After a STORE cycle is initiated, read/write to CY14X256Q is inhibited until the cycle is completed.

The HSB signal or the RDY bit in the Status Register can be monitored by the system to detect if a STORE or Software RECALL cycle is in progress. The busy status of nvSRAM is indicated by HSB being pulled LOW or RDY bit being set to '1'. To avoid unnecessary nonvolatile STOREs, AutoStore and Hardware STORE operations are ignored unless at least one write operation has taken place since the most recent STORE or RECALL cycle. However, software initiated STORE cycles are performed regardless of whether a write operation has taken place.



AutoStore Operation

The AutoStore operation is a unique feature of nvSRAM, which automatically stores the SRAM data to QuantumTrap cells during power-down. This STORE makes use of an external capacitor (V_{CAP}) and enables the device to safely STORE the data in the nonvolatile memory when power goes down.


During normal operation, the device draws current from V_{CC} to charge the capacitor connected to the V_{CAP} pin. When the voltage on the V_{CC} pin drops below V_{SWITCH} during power-down, the device inhibits all memory accesses to nvSRAM and automatically performs a conditional STORE operation using the charge from the V_{CAP} capacitor. The AutoStore operation is not initiated if no write cycle has been performed since last RECALL.

Note If a capacitor is not connected to V_{CAP} pin, AutoStore must be disabled by issuing the AutoStore Disable instruction (AutoStore Disable (ASDISB) Instruction on page 15). If AutoStore is enabled without a capacitor on the V_{CAP} pin, the device attempts an AutoStore operation without sufficient charge to complete the STORE. This will corrupt the data stored in nvSRAM, Status Register as well as the serial number and it will unlock the SNL bit. To resume normal functionality, the WRSR instruction must be issued to update the nonvolatile bits BP0, BP1, and WPEN in the Status Register.

Figure 3 shows the proper connection of the storage capacitor (V_{CAP}) for AutoStore operation. See DC Electrical Characteristics on page 20 for the size of the V_{CAP}

Note CY14X256Q1A does not support AutoStore operation. You must perform Software STORE operation by using the SPI STORE instruction to secure the data.

Figure 3. AutoStore Mode



Software STORE Operation

Software STORE enables the user to trigger a STORE operation through a special SPI instruction. STORE operation is initiated by executing STORE instruction irrespective of whether a write has been performed since the last NV operation.

A STORE cycle takes t_{STORE} time to complete, during <u>whi</u>ch all the memory accesses to nv<u>SRA</u>M are inhibited. The RDY bit of the Status Register or the HSB pin may be polled to find the Ready or Busy status of the nvSRAM. After the t_{STORE} cycle time

is completed, the SRAM is activated again for read and write operations.

Hardware STORE and HSB pin Operation

The $\overline{\text{HSB}}$ pin in CY14X256Q3A is used to control and acknowledge STORE operations. If no STORE or RECALL is in progress, this pin can be used to request a Hardware STORE cycle. When the HSB pin is driven LOW, nvSRAM conditionally initiates a STORE operation after t_{DELAY} duration. A STORE cycle starts only if a write to the SRAM has been performed since the last STORE or RECALL cycle. Reads and Writes to the memory are inhibited for t_{STORE} duration or as long as HSB pin is LOW. The HSB pin also acts as an open drain driver (internal 100 k Ω weak pull-up resistor) that is internally driven LOW to indicate a busy condition when the STORE (initiated by any means) is in progress.

Note After each Hardware and Software STORE operation $\overline{\text{HSB}}$ is driven HIGH for a short time (t_{HHHD}) with standard output high current and then remains HIGH by an internal 100 k Ω pull-up resistor.

Note For successful last data byte STORE, a hardware STORE should be initiated at least one clock cycle after the last data bit D0 is received.

Upon completion of the STORE operation, the nvSRAM memory access is inhibited for t_{LZHSB} time after HSB pin returns HIGH. The HSB pin must be left unconnected if not used.

Note CY14X256Q1A/CY14X256Q2A do not have HSB pin. RDY bit of the SPI Status Register may be probed to determine the Ready or Busy status of nvSRAM.

RECALL Operation

A RECALL operation transfers the data stored in the nonvolatile Quantum rap elements to the SRAM. A RECALL may be initiated in two ways: Hardware RECALL, initiated on power-up and Software RECALL, initiated by a SPI RECALL instruction.

Internally, RECALL is a two step procedure. First, the SRAM data is cleared. Next, the nonvolatile information is transferred into the SRAM cells. All memory accesses are inhibited while a RECALL cycle is in progress. The RECALL operation does not alter the data in the nonvolatile elements.

Hardware RECALL (Power-Up)

During power-up, when $V_{\rm CC}$ crosses $V_{\rm SWITCH}$, an automatic RECALL sequence is initiated, which transfers the content of nonvolatile memory on to the SRAM. The data would previously have been stored on the nonvolatile memory through a STORE sequence.

A Power-Up RECALL cycle takes t_{FA} time to complete and the memory access is disabled during this time. HSB pin is used to detect the ready status of the device.

Software RECALL

Software RECALL allows you to initiate a RECALL operation to restore the content of nonvolatile memory on to the SRAM. A Software RECALL is issued by using the SPI instruction for RECALL.

A Software RECALL takes $t_{\mbox{\scriptsize RECALL}}$ time to complete during which all memory accesses to nvSRAM are inhibited. The



controller must provide sufficient delay for the RECALL operation to complete before issuing any memory access instructions.

Disabling and Enabling AutoStore

If the application does not require the AutoStore feature, it can be disabled by using the ASDISB instruction. If this is done, the nvSRAM does not perform a STORE operation at power-down.

AutoStore can be re-enabled by using the ASENB instruction. However, these operations are not nonvolatile and if you need this setting to survive the power cycle, a STORE operation must be performed following AutoStore Disable or Enable operation.

Note CY14X256Q2A/CY14X256Q3A comes from the factory with AutoStore enabled and CY14X256Q1A/CY14X256Q2A/CY14X256Q3A comes from the factory with 0x00 written in all cells. In CY14X256Q1A, V_{CAP} pin is not present and AutoStore option is not available. The AutoStore Enable and Disable instructions to CY14X256Q1A are ignored.

Note If AutoStore is disabled and V_{CAP} is not required, then the V_{CAP} pin must be left open. The V_{CAP} pin must never be connected to ground. The Power-Up RECALL operation cannot be disabled in any case.

Serial Peripheral Interface

SPI Overview

The SPI is a four-pin interface with Chip Select (\overline{CS}), Serial Input (SI), Serial Output (SO), and Serial Clock (SCK) pins. CY14X256Q provides serial access to nvSRAM through SPI interface. The SPI bus on CY14X256Q can run at speeds up to 104 MHz except READ instruction.

The SPI is a synchronous serial interface which uses clock and data pins for memory access and supports multiple devices on the data bus. A device on SPI bus is activated using the CS pin.

The relationship between chip select, clock, and data is dictated by the SPI mode. This device supports SPI modes 0 and 3. In both these modes, data is clocked into the nvSRAM on $\underline{\text{the}}$ rising edge of SCK starting from the first rising edge after $\overline{\text{CS}}$ goes active.

The SPI protocol is controlled by opcodes. These opcodes specify the commands from the bus master to the slave device. After \overline{CS} is activated the first byte transferred from the bus master is the opcode. Following the opcode, any addresses and data are then transferred. The \overline{CS} must go inactive after an operation is complete and before a new opcode can be issued. The commonly used terms used in SPI protocol are given below:

SPI Master

The SPI master device controls the operations on a SPI bus. A SPI bus may have only one master with one or more slave devices. All the slaves share the same SPI bus lines and the master may select any of the slave devices using the \overline{CS} pin. All the operations must be initiated by the master activating a slave device by pulling the \overline{CS} pin of the slave LOW. The master also generates the SCK and all the data transmission on SI and SO lines are synchronized with this clock.

SPI Slave

The SPI slave device is activated by the master through the Chip Select line. A slave device gets the SCK as an input from the SPI master and all the communication is synchronized with this clock. SPI slave never initiates a communication on the SPI bus and acts on the instruction from the master.

CY14X256Q operates as a SPI slave and may share the SPI bus with other SPI slave devices.

Chip Select (CS)

For selecting any slave device, the master needs to pull-down the corresponding CS pin. Any instruction can be issued to a slave device only while the CS pin is LOW. When the device is not selected, data through the SI pin is ignored and the serial output pin (SO) remains in a high impedance state.

Note A new instruction must begin with the falling edge of CS. Therefore, only one opcode can be issued for each active Chip Select cycle.

Serial Clock (SCK)

Serial clock is generated by the SPI master <u>and</u> the communication is synchronized with this clock after CS goes LOW.

CY14X256Q enables SPI modes 0 and 3 for data communication. In both these modes, the inputs are latched by the slave device on the rising edge of SCK and outputs are issued on the falling edge. Therefore, the first rising edge of SCK signifies the arrival of the first bit (MSB) of SPI instruction on the SI pin. Further, all data inputs and outputs are synchronized with SCK

Data Transmission - SI/SO

SPI data bus consists of two lines, SI and SO, for serial data communication. The SI is also referred to as Master Out Slave In (MOSI) and SO is referred to as Master In Slave Out (MISO). The master issues instructions to the slave through the SI pin, while the slave responds through the SO pin. Multiple slave devices may share the SI and SO lines as described earlier.

CY14X256Q has two separate pins for SI and SO, which can be connected with the master as shown in Figure 4 on page 7.

Most Significant Bit (MSB)

The SPI protocol requires that the first bit to be transmitted is the Most Significant Bit (MSB). This is valid for both address and data transmission.

The 256-Kbit serial nvSRAM requires a 2-byte address for any read or write operation. However, because the address is only 15-bits, it implies that the first MSB which is fed in is ignored by the device. Although this bit is 'don't care', Cypress recommends that this bit is treated as 0 to enable seamless transition to higher memory densities.

Serial Opcode

After the slave device is selected with $\overline{\text{CS}}$ going LOW, the first byte received is treated as the opcode for the intended operation. CY14X256Q uses the standard opcodes for memory accesses. In addition to the memory accesses, it provides additional opcodes for the nvSRAM specific functions: STORE, RECALL, AutoStore Enable, and AutoStore Disable. See Table 2 on page



9 for details.


Invalid Opcode

If an invalid opcode is received, the opcode is ignored and the device ignores <u>any</u> additional serial data on the SI pin till the next falling edge of CS and the SO pin remains tristated.

Status Register

CY14X256Q has an 8-bit Status Register. The bits in the Status Register are used to configure the SPI bus. These bits are described in the Table 4 on page 10.

Figure 4. System Configuration Using SPI nvSRAM



SPI Modes

CY14X256Q may be driven by a microcontroller with its SPI peripheral running in either of the following two modes:

- SPI Mode 0 (CPOL = 0, CPHA = 0)
- SPI Mode 3 (CPOL = 1, CPHA = 1)

For both these modes, the input data is latched in on the rising edge of SCK starting from the first rising edge after $\overline{\text{CS}}$ goes active. If the clock starts from a HIGH state (in mode 3), the first rising edge after the clock toggles, is considered. The output data is available on the falling edge of SCK.

The two SPI modes are shown in Figure 5 and Figure 6. The status of clock when the bus master is in standby mode and not transferring data is:

- SCK remains at 0 for Mode 0
- SCK remains at 1 for Mode 3

CPOL and CPHA bits must be set in the SPI controller for either Mode 0 or Mode 3. The device detects the SPI mode from $\underline{\text{the}}$ status of SCK pin when the device is selected by bringing the CS pin LOW. If SCK pin is LOW when the device is selected, SPI Mode 0 is assumed and if SCK pin is HIGH, it works in SPI Mode 3.

Figure 5. SPI Mode 0





Figure 6. SPI Mode 3





SPI Operating Features

Power-Up

Power-up is defined as the condition when the power supply is turned on and V_{CC} crosses V_{switch} voltage.

As described earlier, at power-up nvSRAM performs a Power-Up RECALL operation for t_{FA} duration during which, all memory accesses are disabled. The HSB pin can be probed to check the Ready/Busy status of nvSRAM after power-up.

The following are the device status after power-up.

- Selected (Active power mode) if CS pin is LOW
- Deselected (Standby power mode) if CS pin is HIGH
- Not in the Hold condition
- Status Register state:
 - □ Write Enable (WEN) bit is reset to '0'
 - □ WPEN, BP1, BP0 unchanged from previous STORE operation.

The WPEN, BP1, and BP0 bits of the Status Register are nonvolatile bits and remain unchanged from the previous STORE operation.

Power-Down


At power-down (continuous decay of V_{CC}), when V_{CC} drops from the normal operating voltage and below the V_{SWITCH} threshold

voltage, the device stops responding to any instruction sent to it. If a write cycle is in progress and the last data bit D0 has been received when the power goes down, it is allowed t_{DELAY} time to complete the write. After this, all memory accesses are inhibited and a conditional AutoStore operation is performed (AutoStore is not performed if no writes have happened since the last RECALL cycle). This feature prevents inadvertent writes to nvSRAM from happening during power-down.

However, to completely avoid the possibility of inadvertent writes during power-down, ensure that the device is deselected and is in standby power mode, and the $\overline{\text{CS}}$ follows the voltage applied on V_{CC} .

Active Power and Standby Power Modes

When $\overline{\text{CS}}$ is LOW, the device is selected and is in the active power mode. The device consumes I_{CC} current, as specified in DC Electrical Characteristics on page 20. When $\overline{\text{CS}}$ is HIGH, the device is deselected and the device goes into the standby power mode after t_{SB} time if a STORE or RECALL cycle is not in progress. If a STORE/RECALL cycle is in progress, the device goes into the standby power mode after the STORE or RECALL cycle is completed. In the standby power mode, the current drawn by the device drops to I_{SB}.





SPI Functional Description

The CY14X256Q uses an 8-bit instruction register. Instructions and their opcodes are listed in Table 2. All instructions, addresses, and data are transferred with the MSB first and start

with a HIGH to LOW $\overline{\text{CS}}$ transition. There are, in all, 18 SPI instructions which provide access to most of the functions in nvSRAM. Further, the WP, HOLD and HSB pins provide additional functionality driven through hardware.

Table 2. Instruction Set

Instruction Category	Instruction Name	Opcode	Operation
Status Register Control Instru	ctions		
	RDSR	0000 0101	Read Status Register
Status Register access	FAST_RDSR	0000 1001	Fast Status Register read - SPI clock > 40 MHz
	WRSR	0000 0001	Write Status Register
Write protection and block pro-	WREN	0000 0110	Set write enable latch
tection	WRDI	0000 0100	Reset write enable latch
SRAM Read/Write Instructions			
	READ	0000 0011	Read data from memory array
Memory access	FAST_READ	0000 1011	Fast read - SPI clock > 40 MHz
	WRITE	0000 0010	Write data to memory array
Special NV Instructions			•
	STORE	0011 1100	Software STORE
nySBAM anagial functions	RECALL	0110 0000	Software RECALL
nvSRAM special functions	ASENB	0101 1001	AutoStore Enable
	ASDISB	0001 1001	AutoStore Disable
Special Instructions			
Sleep	SLEEP	1011 1001	Sleep mode enable
	WRSN	1100 0010	Write serial number
Serial number	RDSN	1100 0011	Read serial number
	FAST_RDSN	1100 1001	Fast serial number read - SPI clock > 40 MHz
	RDID	1001 1111	Read manufacturer JEDEC ID and product ID
Device ID read	FAST_RDID	1001 1001	Fast manufacturer JEDEC ID and product ID Read - SPI clock > 40 MHz
Reserved	- Reserved -	0001 1110	

The SPI instructions are divided based on their functionality in the following types:

- ☐ Status Register control instructions:
 - Status Register access: RDSR, FAST_RDSR and WRSR instructions
 - Write protection and block protection: WREN and WRDI instructions along with WP pin and WEN, BP0, and BP1 bits
- □ SRAM read/write instructions
 - Memory access: READ, FAST_READ and WRITE instructions

- ☐ Special NV instructions
 - nvSRAM special instructions: STORE, RECALL, ASENB, and ASDISB
- □ Special instructions
 - SLEEP, WRSN, RDSN, FAST_RDSN, RDID, FAST_RDID



Status Register

The Status Register bits <u>are listed in Table 3</u>. The Status Register consists of a Ready bit (RDY) and data protection bits BP1, BP0, WEN, and WPEN. The RDY bit can be polled to check the Ready or Busy status while a nvSRAM STORE or Software RECALL cycle is in progress. The Status Register can be modified by WRSR instruction and read by RDSR or FAST_RDSR instruction. However, only the WPEN, BP1, and BP0 bits of the Status Register can be modified by using the WRSR instruction. The WRSR instruction has no effect on WEN and RDY bits. The

default value shipped from the factory for WEN, BP0, BP1, bits 4–5, SNL and WPEN is '0'.

SNL (bit 6) of the Status Register is used to lock the serial number written using the WRSN instruction. The serial number can be written using the WRSN instruction multiple times while this bit is still '0'. When set to '1', this bit prevents any modification to the serial number. This bit is factory programmed to '0' and can only be written to once. After this bit is set to '1', it can never be cleared to '0'.

Table 3. Status Register Format

Bit 7	Bit 6	Bit 5	Bit 4	Bit 3	Bit 2	Bit 1	Bit 0
WPEN (0)	SNL (0)	X (0)	X (0)	BP1 (0)	BP0 (0)	WEN (0)	RDY

Table 4. Status Register Bit Definition

Bit	Definition	Description
Bit 0 (RDY)	Ready	Read only bit indicates the ready status of device to perform a memory access. This bit is set to '1' by the device while a STORE or Software RECALL cycle is in progress.
Bit 1 (WEN)		WEN indicates if the device is write enabled. This bit defaults to '0' (disabled) on power-up. WEN = '1'> Write enabled WEN = '0'> Write disabled
Bit 2 (BP0)	Block Protect bit '0'	Used for block protection. For details see Table 5 on page 12.
Bit 3 (BP1)	Block Protect bit '1'	Used for block protection. For details see Table 5 on page 12.
Bit 4-5	Don't care	These bits are non-writable and always return '0' upon read.
Bit 6 (SNL)	Serial Number Lock	Set to '1' for locking serial number
Bit 7 (WPEN)	Write Protect Enable bit	Used for enabling the function of Write Protect Pin (WP). For details see Table 6 on page 12.

Read Status Register (RDSR) Instruction

The Read Status Register instruction provides access to the Status Register at SPI frequency up to 40 MHz. This instruction is used to probe the Write Enable status of the device or the Ready status of the device. RDY bit is set by the device to 1 whenever a STORE or Software RECALL cycle is in progress. The block protection and WPEN bits indicate the extent of protection employed.

This instruction is issued after the falling edge of $\overline{\text{CS}}$ using the opcode for RDSR.

Fast Read Status Register (FAST_RDSR) Instruction

The FAST_RDSR instruction allows you to read the Status Register at a SPI frequency above 40 MHz and up to 104 MHz (max). This instruction is used to probe the Write Enable status of the device or the Ready status of the device. RDY bit is set by the device to 1 whenever a STORE or Software RECALL cycle is in progress. The block protection and WPEN bits indicate the extent of protection employed.

This instruction is issued after the falling edge of \overline{CS} using the opcode for RDSR followed by a dummy byte.

Write Status Register (WRSR) Instruction

The WRSR instruction enables the user to write to the Status Register. However, this instruction cannot be used to modify bit 0 (RDY), bit 1 (WEN) and bits 4–5. The BPO and BP1 bits can be used to select one of four levels of block protection. Further, WPEN bit must be set to '1' to enable the use of Write Protect (WP) pin.

WRSR instruction is a write instruction and needs writes to be enabled (WEN bit set to '1') using the WREN instruction before it is issued. The instruction is issued after the falling edge of CS using the opcode for WRSR followed by eight bits of data to be stored in the Status Register. WRSR instruction can be used to modify only bits 2, 3, 6, and 7 of the Status Register.

Note In CY14X256Q, the values written to Status Register are saved to nonvolatile memory only after a STORE operation. If AutoStore is disabled (or while using CY14X256Q1A), any modifications to the Status Register must be secured by performing a Software STORE operation.

Note CY14X256Q2A does not have $\overline{\text{WP}}$ pin. Any modification to bit 7 of the Status Register has no effect on the functionality of CY14X256Q2A.



Figure 7. Read Status Register (RDSR) Instruction Timing




Figure 8. Fast Read Status Register (FAST_RDSR) Instruction Timing





Figure 9. Write Status Register (WRSR) Instruction Timing





Write Protection and Block Protection

CY14X256Q provides features for both software and hardware write protection using WRDI instruction and WP. Additionally, this device also provides block protection mechanism through BP0 and BP1 pins of the Status Register.


The write enable and disable status of the device is indicated by WEN bit of the Status Register. The write instructions (WRSR WRITE and WRSN) and nvSRAM special instruction (STORE, RECALL, ASENB and ASDISB) need the write to be enabled (WEN bit = '1') before they can be issued.

Write Enable (WREN) Instruction

On power-up, the device is always in the write disable state. The following WRITE, WRSR, WRSN, or nvSRAM special instruction must therefore be preceded by a Write Enable instruction. If the device is not write enabled (WEN = '0'), it ignores the write instructions and returns to the standby state when CS is brought HIGH. A new CS falling edge is required to re-initiate serial communication. The instruction is issued following the falling edge of CS. When this instruction is used, the WEN bit of Status Register is set to '1'. WEN bit defaults to '0' on power-up.

Note After completion of a write instruction (WRSR, WRITE and WRSN) or nvSRAM special instruction (STORE, RECALL, ASENB, and ASDISB) instruction, WEN bit is cleared to '0'. This is done to provide protection from any inadvertent writes. Therefore, WREN instruction needs to be used before a new write instruction is issued.


Figure 10. WREN Instruction



Write Disable (WRDI) Instruction

Write Disable instruction disables the write by clearing the WEN bit to '0' in order to protect the device against inadvertent writes. This instruction is issued following the falling edge of CS followed by opcode for WRDI instruction. The WEN bit is cleared on the rising edge of CS following a WRDI instruction.

Figure 11. WRDI Instruction



Block Protection

Block protection is provided using the BP0 and BP1 pins of the Status Register. These bits can be set using WRSR instruction and probed using the RDSR instruction. The nvSRAM is divided into four array segments. One-quarter, one-half, or all of the memory segments can be protected. Any data within the protected segment is read only. Table 5 shows the function of Block Protect bits.

Table 5. Block Write Protect Bits

Level	Status Register Bits		Array Addresses Protected
	BP1	BP0	
0	0	0	None
1 (1/4)	0	1	0x6000-0x7FFF
2 (1/2)	1	0	0x4000-0x7FFF
3 (All)	1	1	0x0000-0x7FFF

Hardware Write Protection (WP)

The write protect pin (WP) is used to provide hardware write protection. WP pin enables all normal read and write operations when held HIGH. When the WP pin is brought LOW and WPEN bit is '1', all write operations to the Status Register are inhibited. The hardware write protection function is blocked when the WPEN bit is '0'. This allows you to install the device in a system with the WP pin tied to ground, and still write to the Status Register.

WP pin can be used along with WPEN and Block Protect bits (BP1 and BP0) of the Status Register to inhibit writes to memory. When WP pin is LOW and WPEN is set to '1', any modifications to the Status Register are disabled. Therefore, the memory is protected by setting the BP0 and BP1 bits and the WP pin inhibits any modification of the Status Register bits, providing hardware write protection.

Note WP going LOW when CS is still LOW has no effect on any of the ongoing write operations to the Status Register.

Note CY14X256Q2A does not have WP pin and therefore does not provide hardware write protection.

Table 6 summarizes all the protection features of this device.

Table 6. Write Protection Operation

WPEN	WP	WEN	Protected Blocks	Unprotected Blocks	Status Register
Х	Χ	0	Protected	Protected	Protected
0	Χ	1	Protected	Writable	Writable
1	LOW	1	Protected	Writable	Protected
1	HIGH	1	Protected	Writable	Writable



Memory Access

All memory accesses are done using the READ and WRITE instructions. These instructions cannot be used while a STORE or RECALL cycle is in progress. A STORE cycle in progress is indicated by the RDY bit of the Status Register and the HSB pin.

Read Sequence (READ) Instruction

The read operations on this device are performed by giving the instruction on the SI pin and reading the output on SO pin. The following sequence needs to be followed for a read operation: After the CS line is pulled LOW to select a device, the read opcode is transmitted through the SI line followed by two bytes of address. The MSB bit (A15) of the address is a "don't care". After the last address bit is transmitted on the SI pin, the data (D7-D0) at the specific address is shifted out on the SO line on the falling edge of SCK starting with D7. Any other data on SI line after the last address bit is ignored.

CY14X256Q allows reads to be performed in bursts through SPI which can be used to read consecutive addresses without issuing a new READ instruction. If only one byte is to be read, the CS line must be driven HIGH after one byte of data comes out. However, the read sequence may be continued by holding the CS line LOW and the address is automatically incremented and data continues to shift out on SO pin. When the last data memory address (0x7FFF) is reached, the address rolls over to 0x0000 and the device continues to read.

Note The READ instruction operates up to a maximum of 40 MHz SPI frequency.

Fast Read Sequence (FAST_READ) Instruction

The FAST_READ instruction allows you to read memory at SPI frequency above 40 MHz and up to 104 MHz (Max). The host system must first select the device by driving CS low, the FAST_READ instruction is then written to SI, followed by 2 address byte and then a dummy byte. The MSB bit (A15) of the address is a "don't care".

From the subsequent falling edge of the SCK, the data of the specific address is shifted out serially on the SO line starting with

MSB. The first byte specified can be at any location. The device automatically increments to the next higher address after each byte of data is output. The entire memory array can therefore be read with a single FAST_READ instruction. When the highest address in the memory array is reached, address counter rolls over to start address 0x0000 and thus allowing the read sequence to continue indefinitely. The FAST_READ instruction is terminated by driving CS High at any time during data output.


Note FAST_READ instruction operates up to maximum of 104 MHz SPI frequency.

Write Sequence (WRITE) Instruction


The write operations on this device are performed through the SI pin. To perform a write operation, if the device is write disabled, then the device must first be write enabled through the WREN instruction. When the writes are enabled (WEN = '1'), WRITE instruction is issued after the falling edge of CS. A WRITE instruction constitutes transmitting the WRITE opcode on SI line followed by two bytes of address and the data (D7-D0) which is to be written. The MSB bit (A15) of the address is a "don't care".

CY14X256Q enables writes to be performed in bursts through SPI which can be used to write consecutive addresses without issuing a new WRITE instruction. If only one byte is to be written, the CS line must be driven HIGH after the D0 (LSB of data) is transmitted. However, if more bytes are to be written, CS line must be held LOW and address is incremented automatically. The following bytes on the SI line are treated as data bytes and written in the successive addresses. When the last data memory address (0x7FFF) is reached, the address rolls over to 0x0000 and the device continues to write. The WEN bit is reset to '0' on completion of a WRITE sequence.

Note When a burst write reaches a protected block address, it continues the address increment into the protected space but does not write any data to the protected memory. If the address roll over takes the burst write to unprotected space, it resumes writes. The same operation is true if a burst write is initiated within a write protected block.









nvSRAM Special Instructions

CY14X256Q provides four special instructions which enables access to the nvSRAM specific functions: STORE, RECALL, ASDISB, and ASENB, Table 7 lists these instructions.

Table 7. nvSRAM Special Instructions


Function Name	Opcode	Operation
STORE	0011 1100	Software STORE
RECALL	0110 0000	Software RECALL
ASENB	0101 1001	AutoStore Enable
ASDISB	0001 1001	AutoStore Disable

Software STORE (STORE) Instruction

When a STORE instruction is executed, nvSRAM performs a Software STORE operation. The STORE operation is performed irrespective of whether a write has taken place since the last STORE or RECALL operation.

To issue this instruction, the device must be write enabled (WEN bit = '1'). The instruction is performed by transmitting the STORE opcode on the SI pin following the falling edge of CS. The WEN bit is cleared on the positive edge of CS following the STORE instruction.

Figure 17. Software STORE Operation




Software RECALL (RECALL) Instruction

When a RECALL instruction is executed, nvSRAM performs a Software RECALL operation. To issue this instruction, the device must be write enabled (WEN = '1').

The instruction is performed by transmitting the RECALL opcode on the SI pin following the falling edge of CS. The WEN bit is cleared on the positive edge of CS following the RECALL instruction.

Figure 18. Software RECALL Operation




AutoStore Enable (ASENB) Instruction

The AutoStore Enable instruction enables the AutoStore on CY14X256Q2A/CY14X256Q3A. This setting is not nonvolatile and needs to be followed by a STORE sequence to survive the power cycle.

To issue this instruction, the device must be write enabled (WEN = '1'). The instruction is performed by transmitting the ASENB opcode on the SI pin following the falling edge of $\overline{\text{CS}}$. The WEN bit is cleared on the positive edge of $\overline{\text{CS}}$ following the ASENB instruction.

Note If ASDISB and ASENB instructions are executed in CY14X256Q2A/CY14X256Q3A, the device is busy for the duration of software sequence processing time (t_{SS}). However, ASDISB and ASENB instructions have no effect on CY14X256Q1A as AutoStore is internally disabled.

Figure 19. AutoStore Enable Operation




AutoStore Disable (ASDISB) Instruction

AutoStore is enabled by default in CY14X256Q2A/CY14X256Q3A. The ASDISB instruction disables the AutoStore. This setting is not nonvolatile and needs to be followed by a STORE sequence to survive the power cycle.

To issue this instruction, the device must be write enabled (WEN = '1'). The instruction is performed by transmitting the ASDISB opcode on the SI pin following the falling edge of CS. The WEN bit is cleared on the positive edge of CS following the ASDISB instruction.

Figure 20. AutoStore Disable Operation





Special Instructions

SLEEP Instruction

SLEEP instruction puts the nvSRAM in sleep mode. When the SLEEP instruction is issued, the nvSRAM takes t_{SS} time to process the SLEEP request. Once the SLEEP command is successfully registered and processed, the nvSRAM toggles HSB LOW, performs a STORE operation to secure the data to nonvolatile memory and then enters into SLEEP mode. The device starts consuming IZZ current after t_{SLEEP} time from the instance when SLEEP instruction is registered. The device is not accessible for normal operations after SLEEP instruction is issued. Once in sleep mode, the SCK and SI pins are ignored and SO will be Hi-Z but device continues to monitor the CS pin.

To wake the nvSRAM from the sleep mode, the device must be selected by toggling the CS pin from HIGH to LOW. The device wakes up and is accessible for normal operations after twake duration after a falling edge of CS pin is detected.


Note Whenever nvSRAM enters into sleep mode, it initiates nonvolatile STORE cycle which results in an endurance cycle per sleep command execution. A STORE cycle starts only if a write to the SRAM has been performed sin<mark>ce t</mark>he las<mark>t ST</mark>ORE or RECALL cycle.

Figure 21. Sleep Mode Entry

CS

SCK

SO



Op-Code

0

Serial Number


The serial number is an 8 byte programmable memory space provided to you uniquely identify this device. It typically consists of a two byte Customer ID, followed by five bytes of unique serial number and one byte of CRC check. However, nvSRAM does not calculate the CRC and it is up to the system designer to utilize the eight byte memory space in whatever manner desired. The default value for eight byte locations are set to '0x00'.

WRSN (Serial Number Write) Instruction

The serial number can be written using the WRSN instruction. To write serial number the write must be enabled using the WREN instruction. The WRSN instruction can be used in burst mode to write all the 8 bytes of serial number.

The serial number is locked using the SNL bit of the Status Register. Once this bit is set to '1', no modification to the serial number is possible. After the SNL bit is set to '1', using the WRSN instruction has no effect on the serial number.

A STORE operation (AutoStore or Software STORE) is required to store the serial number in nonvolatile memory. If AutoStore is disabled, you must perform a Software STORE operation to secure and lock the serial Number. If SNL bit is set to '1' and is not stored (AutoStore disabled), the SNL bit and serial number defaults to '0' at the next power cycle. If SNL bit is set to '1' and is stored, the SNL bit can never be cleared to '0'. This instruction requires the WEN bit to be set before it can be executed. The WEN bit is reset to '0' after completion of this instruction.



D4 \ D3 \ D2 D7 8-Byte Serial Number


Figure 22. WRSN Instruction



RDSN (Serial Number Read) Instruction

The serial number is read using RDSN instruction at SPI frequency upto 40 MHz. A serial number read may be performed in burst mode to read all the eight bytes at once. After the last byte of serial number is read, the device does not loop back.

RDSN instruction can be issued by shifting the opcode for RDSN in through the SI pin of nvSRAM after CS goes LOW. This is followed by nvSRAM shifting out the eight bytes of serial number through the SO pin.



FAST_RDSN (Fast Serial Number Read) Instruction

The FAST_RDSN instruction is used to read serial number at SPI frequency above 40 MHz and up to 104 MHz (max). A serial number read may be performed in burst mode to read all the eight bytes at once. After the last byte of serial number is read,

the device does not loop back. FAST_RDSN instruction can be issued by shifting the op-code for FAST_RDSN in through the SI pin of nvSRAM followed by dummy byte after CS goes LOW. This is followed by nvSRAM shifting out the eight bytes of serial number through the SO pin.




Figure 24. FAST ROSN Instruction



Device ID

Device ID is 4-byte read only code identifying a type of product uniquely. This includes the product family code, configuration and density of the product.

Table 8. Device ID

		Device ID Description				
Device	Device ID (4 bytes)	31–21 (11 bits)	20–7 (14 bits)	6–3 (4 bits)	2–0 (3 bits)	
		Manufacture ID	Product ID	Density ID	Die Rev	
CY14C256Q1A	0x06810090	00000110100	00001000000001	0010	000	
CY14C256Q2A	0x06818010	00000110100	00001100000000	0010	000	
CY14C256Q3A	0x06818090	00000110100	00001100000001	0010	000	
CY14B256Q1A	0x06810890	00000110100	00001000010001	0010	000	
CY14B256Q2A	0x06818810	00000110100	00001100010000	0010	000	
CY14B256Q3A	0x06818890	00000110100	00001100010001	0010	000	
CY14E256Q1A	0x06811090	00000110100	00001000100001	0010	000	
CY14E256Q2A	0x06819010	00000110100	00001100100000	0010	000	
CY14E256Q3A	0x06819090	00000110100	00001100100001	0010	000	

The device ID is divided into four parts as shown in Table 8:

1. Manufacturer ID (11 bits)

This is the JEDEC assigned manufacturer ID for Cypress. JEDEC assigns the manufacturer ID in different banks. The first three bits of the manufacturer ID represent the bank in which ID is assigned. The next eight bits represent the manufacturer ID.

Cypress's manufacturer ID is 0x34 in bank 0. Therefore the manufacturer ID for all Cypress nvSRAM products is:

Cypress ID - 000 0011 0100

2. Product ID (14 bits)

The product ID is defined as shown in the Table 8

3. Density ID (4 bits)

The 4 bit density ID is used as shown in Table 8 for indicating the 256 Kb density of the product.


4. Die Rev (3 bits)

This is used to represent any major change in the design of the product. The initial setting of this is always 0x0.

RDID (Device ID Read) Instruction

This instruction is used to read the JEDEC assigned manufacturer ID and product ID of the device at SPI frequency upto 40 MHz. This instruction can be used to identify a device on the bus. RDID instruction can be issued by shifting the op-code for RDID in through the SI pin of nvSRAM after CS goes LOW. This is followed by nvSRAM shifting out the four bytes of device ID through the SO pin.

Figure 25. RDID instruction






FAST_RDID (Fast Device ID Read) Instruction

The FAST_RDID instruction allows the user you to read the JEDEC assigned manufacturer ID and product ID at SPI frequency above 40 MHz and up to 104 MHz (max). FAST_RDID

instruction can be issued by shifting the op-code for FAST_RDID in through the SI pin of nvSRAM followed by dummy byte after CS goes LOW. This is followed by nvSRAM shifting out the four bytes of device ID through the SO pin.




HOLD Pin Operation

The HOLD pin is used to pause the serial communication. When the device is selected and a serial sequence is underway, HOLD is used to pause the serial communication with the master device without resetting the ongoing serial sequence. To pause, the HOLD pin must be brought LOW when the SCK pin is LOW. To resume serial communication, the HOLD pin must be brought HIGH when the SCK pin is LOW (SCK may toggle during HOLD). While the device serial communication is paused, inputs to the SI pin are ignored and the SO pin is in the high impedance state.

This pin can be used by the master with the $\overline{\text{CS}}$ pin to pause the serial communication by bringing the pin $\overline{\text{HOLD}}$ LOW and deselecting an SPI slave to establish communication with another slave device, without the serial communication being reset. The communication may be $\underline{\text{resumed}}$ at a later point by selecting the device and setting the $\underline{\text{HOLD}}$ pin HIGH.

Figure 27. HOLD Operation





Maximum Ratings

Exceeding maximum ratings may shorten the useful life of the device. These user guidelines are not tested. Storage temperature-65 °C to +150 °C Maximum accumulated storage time At 150 °C ambient temperature 1000 h At 85 °C ambient temperature 20 Years Maximum junction temperature 150 °C Supply voltage on V_{CC} relative to V_{SS} CY14C256Q: V_{CC} = 2.4 V to 2.6 V ...-0.5 V to +3.1 V CY14B256Q: V_{CC} = 2.7 V to 3.6 V ...-0.5 V to +4.1 V CY14E256Q: V_{CC} = 4.5 V to 5.5 V ...-0.5 V to +7.0 V DC voltage applied to outputs in High Z state-0.5 V to V_{CC} + 0.5 V Input voltage-0.5 V to $V_{CC} + 0.5 \text{ V}$

any pin to ground potential-2.0 V to V_{CC} + 2.0 V

Package power dissipation capability (T _A = 25 °C)1.0 V	٧
Surface mount lead soldering temperature (3 seconds)+260°C)
DC output current (1 output at a time, 1s duration) 15 m/	4
Static discharge voltage (per MIL-STD-883, Method 3015)	
Latch-up current > 140 m/	4

Operating Range

Device	Range	Ambient Temperature	V _{CC}
CY14C256Q	Industrial	–40 °C to +85 °C	2.4 V to 2.6 V
CY14B256Q			2.7 V to 3.6 V
CY14E256Q			4.5 V to 5.5 V

DC Electrical Characteristics

Transient voltage (< 20 ns) on

Over the Operating Range

Parameter	Description	Test Condit	ions	Min	Typ ^[5]	Max	Unit
V _{CC}	Power supply		CY14C256Q	2.4	2.5	2.6	V
			CY14B256Q	2.7	3.0	3.6	V
			CY14E256Q	4.5	5.0	5.5	V
I _{CC1}	Average V _{CC} current	f _{SCK} = 40 MHz; Values obtained	CY14C256Q	-	-	3	mA
		without output loads	CY14B256Q				
		$(I_{OUT} = 0 \text{ mA})$	CY14E256Q	-	-	4	mA
		f _{SCK} = 104 MHz; Valu without output loads (es obtained l _{OUT} = 0 mA)	-	1	10	mA
I _{CC2}	Average V _{CC} current during STORE	All inputs don't care, \ Average current for d	/ _{CC} = Max uration t _{STORE}	-	-	3	mA
I _{CC3}	Average V _{CC} current f _{SCK} = 1 MHz; V _{CC} = V _{CC(Typ)} , 25 °C	All inputs cycling at C Values obtained witho loads (I _{OUT} = 0 mA)	-	_	1	mA	
I _{CC4}	Average V _{CAP} current during AutoStore cycle	All inputs don't care. A current for duration t _S	Average TORE	-	1	3	mA
I _{SB}	V _{CC} standby current				150	μА	
I _{ZZ}	Sleep mode current	t _{SLEEP} time after SLEE is registered. All input and configured at CM	EP Instruction s are static OS logic level.	_	1	8	μА
I _{IX} ^[6]	Input leakage current (except HSB)			– 1	-	+1	μА
	Input leakage current (for HSB)			-100	_	+1	μА
I_{OZ}	Off-state output leakage current			-1	_	+1	μΑ

Typical values are at 25 °C, $V_{CC} = V_{CC(Typ)}$. Not 100% tested.
The HSB pin has $I_{OUT} = -2 \mu A$ for V_{OH} of 2.4 V when both active high and LOW drivers are disabled. When they are enabled standard V_{OH} and V_{OL} are valid. This parameter is characterized but not tested.



DC Electrical Characteristics (continued)

Over the Operating Range

Parameter	Description	Test Condit	ions	Min	Typ ^[5]	Max	Unit
V _{IH}	Input HIGH voltage		CY14C256Q	1.7		V _{CC} + 0.5	V
			CY14B256Q	2.0	_	V _{CC} + 0.5	V
			CY14E256Q				
V_{IL}	Input LOW voltage		CY14C256Q	$V_{ss} - 0.5$	_	0.7	V
			CY14B256Q	$V_{ss} - 0.5$	_	0.8	V
			CY14E256Q				
V _{OH}	Output HIGH voltage	I _{OUT} = -1 mA	CY14C256Q	2.0	_	-	V
		I _{OUT} = -2 mA	CY14B256Q	2.4	_	-	V
			CY14E256Q	$V_{CC} - 0.4$	_	-	
V_{OL}	Output LOW voltage	I _{OUT} = 2 mA	CY14C256Q	_	_	0.4	V
		I _{OUT} = 4 mA	CY14B256Q	-	_	0.4	V
			CY14E256Q				
V _{CAP} ^[7]	Storage capacitor	Between V _{CAP} pin	CY14C256Q	170	220	270	μF
		and V _{SS}	CY14B256Q	42	47	180	μF
			CY14E256Q				
V _{VCAP} ^[8, 9]	Maximum voltage driven on V _{CAP}	V _{CC} = Max	CY14C256Q	_	_	V _{CC}	V
	pin by the device		CY14B256Q				
			CY14E256Q	_	_	V _{CC} - 0.5	V

Data Retention and Endurance

Over the Operating Range

Parameter	Description						Min	Unit	
DATA _R	Data retention							20	Years
NV_C	Nonvolatile STORE operations							1,000	K

Capacitance

Parameter [9]	Description	Test Condition	Max	Unit	
C _{IN}	Input capacitance	$T_A = 25 ^{\circ}\text{C}, f = 1 \text{MHz},$		7	pF
C _{OUT}	Output pin capacitance	$V_{CC} = V_{CC}$ (Typ)		7	pF

Thermal Resistance

Parameter [9]	Description	Test Conditions	8-pin SOIC	16-pin SOIC	Unit
1 - J/A		Test conditions follow standard test methods and procedures for measuring		56.68	°C/W
$\Theta_{\sf JC}$	Thermal resistance (junction to case)	thermal impedance, per EIA / JESD51.	37.86	32.11	°C/W

Notes

- 7. Min V_{CAP} value guarantees that there is a sufficient charge available to complete a successful AutoStore operation. Max V_{CAP} value guarantees that the capacitor on V_{CAP} is charged to a minimum voltage during a Power-Up RECALL cycle so that an immediate power-down cycle can complete a successful AutoStore. Therefore it is always recommended to use a capacitor within the specified min and max limits. See application note AN43593 for more details on V_{CAP} options.
- Maximum voltage on V_{CAP} pin (V_{VCAP}) is provided for guidance when choosing the V_{CAP} capacitor. The voltage rating of the V_{CAP} capacitor across the operating temperature range should be higher than the V_{VCAP} voltage.
- 9. These parameters are guaranteed by design and are not tested.



AC Test Loads and Waveforms

For 2.5 V (CY14C256Q):

Figure 28. AC Test Loads and Waveforms



For 3 V (CY14B256Q):



For 5 V (CY14E256Q):



AC Test Conditions

	CY14C256Q	CY14B256Q	CY14E256Q
Input pulse levels	0 V to 2.5 V	0 V to 3 V	0 V to 3 V
Input rise and fall times (10%–90%)	<u><</u> 3 ns	≤ 3 ns	≤ 3 ns
Input and output timing reference levels	1.25 V	1.5 V	1.5 V



AC Switching Characteristics

Over the Operating Range

Parame	eters [10]		40 [MHz	104	MHz	
Cypress Parameter	Alt. Parameter	Description	Min	Max	Min	Max	Unit
f _{SCK}	f _{SCK}	Clock frequency, SCK	_	40	_	104	MHz
t _{CL} [11]	t _{WL}	Clock pulse width LOW	11	_	4.5	_	ns
t _{CH} ^[11]	t _{WH}	Clock pulse width HIGH	11	_	4.5	_	ns
t _{CS}	t _{CE}	CS HIGH time	20	_	20	_	ns
t _{CSS}	t _{CES}	CS setup time	10	_	5	_	ns
t _{CSH}	t _{CEH}	CS hold time	10	_	5	_	ns
t _{SD}	t _{SU}	Data in setup time	5	ı	4	1	ns
t _{HD}	t _H	Data in hold time	5	-	3	1	ns
t _{HH}	t _{HD}	HOLD hold time	5	_	3	_	ns
t _{SH}	t _{CD}	HOLD setup time	5	ı	3	1	ns
t _{CO}	t _V	Output Valid	_	9	-	8	ns
t _{HHZ} ^[11]	t _{HZ}	HOLD to output HIGH Z	_	15	_	8	ns
t _{HLZ} [11]	t _{LZ}	HOLD to output LOW Z	_	15	_	8	ns
t _{OH}	t _{HO}	Output hold time	0	ı	0	1	ns
t _{HZCS} ^[11]	t _{DIS}	Output disable time	-	20	_	8	ns

Notes


^{10.} Test conditions assume signal transition time of 3 ns or less, timing reference levels of V_{CC}/2, input pulse levels of 0 to V_{CC} (typ), and output loading of the specified I_{OL}/I_{OH} and load capacitance shown in Figure 28.

11. These parameters are guaranteed by design and are not tested.



Switching Waveforms

Figure 29. Synchronous Data Timing (Mode 0)





AutoStore or Power-Up RECALL

Over the Operating Range

Parameter	Description		CY142	X256Q	Unit
	Description	Min	Max	Oilit	
t _{FA} [12]	Power-Up RECALL duration	CY14C256Q	_	40	ms
		CY14B256Q	_	20	ms
		CY14E256Q	_	20	ms
t _{STORE} [13]	STORE cycle duration		_	8	ms
t _{DELAY} [14]	Time allowed to complete SRAM write cycle		_	25	ns
V _{SWITCH}	Low voltage trigger level	CY14C256Q	_	2.35	V
		CY14B256Q	_	2.65	V
		CY14E256Q	-	4.40	V
t _{VCCRISE} ^[15]	V _{CC} rise time		150	_	μS
V _{HDIS} ^[15]	HSB output disable voltage		_	1.9	V
t _{I ZHSB} ^[15]	HSB high to nvSRAM active time		-	5	μS
t _{HHHD} ^[15]	HSB high active time		_	500	ns
t _{WAKE}	Time for nvSRAM to wake up from SLEEP mode	CY14C256Q	_	40	ms
		CY14B256Q	_	20	ms
		CY14E256Q	_	20	ms
t _{SLEEP}	Time to enter SLEEP mode after issuing SLEEP instruction	•	_	8	ms
t _{SB} ^[15]	Time to enter into standby mode after CS going HIGH		_	100	μs

Switching Waveforms

Figure 31. AutoStore or Power-Up RECALL [16] V_{CC} V_{SWITCH} $V_{\rm HDIS}$ Note¹³ Note 13 t_{VCCRISE} tSTORE t_{HHHD} . t_{HHHD} Note 17 Note 17 HSB OUT DELAY t_{LZHSB} LZHSB AutoStore POWER-UP RECALL t_{FA} t_{FA} Read & Write Inhibited (RWI) POWER-UP Read & Write **BROWN** POWER-UP Read & Write **POWER RECALL** OUT **DOWN RECALL** AutoStore AutoStore

- 12. t_{FA} starts from the time V_{CC} rises above V_{SWITCH}.
 13. If an SRAM write has not taken place since the last nonvolatile cycle, AutoStore or Hardware STORE is not initiated.
- 14. On a Hardware STORE, Software STORE / RECALL, AutoStore Enable / Disable and AutoStore initiation, SRAM operation continues to be enabled for time to be ena
- 15. These parameters are guaranteed by design and are not tested.
- 16. Read and Write cycles are ignored during STORE, RECALL, and while V_{CC} is below V_{SWITCH}.

 17. During power-up and power-down, HSB glitches when HSB pin is pulled up through an external resistor.



Software Controlled STORE and RECALL Cycles

Over the Operating Range

Parameter	Description		(256Q	Unit
	Description	Min	Max	Unit
t _{RECALL}	RECALL duration	_	600	μS
t _{SS} [18, 19]	Soft sequence processing time	_	500	μS

Switching Waveforms

Figure 32. Software STORE Cycle^[19]




Figure 33. Software RECALL Cycle^[19]




Figure 34. AutoStore Enable Cycle





Figure 35. AutoStore Disable Cycle



Notes

^{18.} This is the amount of time it takes to take action on a soft sequence command. Vcc power must remain HIGH to effectively register command.

^{19.} Commands such as STORE and RECALL lock out I/O until operation is complete which further increases this time. See the specific command.



Hardware STORE Cycle

Over the Operating Range


Parameter	Description	CY14C256Q3A/ CY14E2	Unit	
		Min	Max	
t _{PHSB}	Hardware STORE pulse width	15	-	ns

Switching Waveforms

Figure 36. Hardware STORE Cycle [20]

Write Latch set HSB (IN) tSTORE tHHHD tLZHSB

Write Latch not set



 $\overline{\text{HSB}}$ pin is driven $\underline{\text{HIGH}}$ to $\overline{\text{V}_{CC}}$ only by Internal 100 KΩ resistor, $\overline{\text{HSB}}$ driver is disabled SRAM is disabled as long as $\overline{\text{HSB}}$ (IN) is driven LOW.

Note

20. If an SRAM write has not taken place since the last nonvolatile cycle, AutoStore or Hardware STORE is not initiated.




Ordering Information

Ordering Code	Package Diagram	Package Type	Operating Range
CY14B256Q2A-SXIT		8-pin SOIC (with V _{CAP}), 40 MHz (Not	Industrial
CY14B256Q2A-SXI		Recommended for New Design)	
CY14E256Q2A-SXIT			
CY14E256Q2A-SXI			

All these parts are Pb-free. This table contains final information. Contact your local Cypress sales representative for availability of these parts.


Ordering Code Definitions





Package Diagrams


Figure 37. 8-pin SOIC (150 Mils) S0815/SZ815/SW815 Package Outline, 51-85066





Package Diagrams (continued)

Figure 38. 16-pin SOIC (0.413 × 0.299 × 0.0932 Inches) Package Outline, 51-85022






Acronyms

Acronym	Description
СРНА	Clock Phase
CPOL	Clock Polarity
CMOS	Complementary Metal Oxide Semiconductor
CRC	Cyclic Redundancy Check
EEPROM	Electrically Erasable Programmable Read-Only Memory
EIA	Electronic Industries Alliance
I/O	Input/Output
JEDEC	Joint Electron Devices Engineering Council
LSB	Least Significant Bit
MSB	Most Significant Bit
nvSRAM	non-volatile Static Random Access Memory
RWI	Read and Write Inhibit
RoHS	Restriction of Hazardous Substances
SNL	Serial Number Lock
SPI	Serial Peripheral Interface
SONOS	Silicon-Oxide-Nitride-Oxide Semiconductor
SOIC	Small Outline Integrated Circuit
SRAM	Static Random Access Memory

Document Conventions

Units of Measure

Symbol	Unit of Measure
°C	degree Celsius
Hz	hertz
kHz	kilohertz
ΚΩ	kilohm
Mbit	megabit
MHz	megahertz
μΑ	microampere
μF	microfarad
μS	microsecond
mA	milliampere
ms	millisecond
ns	nanosecond
Ω	ohm
%	percent
pF	picofarad
V	volt
W	watt






Document History Page

	cument Title: CY14C256Q/CY14B256Q/CY14E256Q, 256-Kbit (32K × 8) SPI nvSRAM cument Number: 001-65282				
Rev.	ECN No.	Orig. of Change	Submission Date	Description of Change	
**	3096371	GVCH	12/08/2010	New data sheet.	
*A	3217968	GVCH	04/06/2011	Updated Device Operation: Updated AutoStore Operation: Updated description. Updated Hardware STORE and HSB pin Operation: Updated description (Added more clarity on HSB pin operation). Updated Status Register: Updated Table 4 (Updated details in "Description" column corresponding to Bit 4–5). Updated DC Electrical Characteristics: Added details of I _{CC1} parameter corresponding to Test Condition "f _{SCK} = 104 MHz". Updated AutoStore or Power-Up RECALL: Updated details in "Description" column corresponding to t _{LZHSB} parameter	
*B	3247264	GVCH	05/03/2011	Changed status from Preliminary to Final. Updated Ordering Information: Updated part numbers.	
*C	3385463	GVCH	09/28/2011	Updated SPI Operating Features: Updated Power-Up: Updated description. Updated Special Instructions: Updated SLEEP Instruction: Updated description. Updated Figure 21. Updated Device ID: Updated Table 8: Added a column "Device ID (4 bytes)" and added details. Updated DC Electrical Characteristics: Changed maximum value of I _{CC2} parameter from 2 mA to 3 mA. Added Note 7 and referred the same note in V _{CAP} parameter. Updated AC Switching Characteristics: Added Note 10 and referred the same note in "Parameter" column. Completing Sunset Review.	
*D	3533222	GVCH	03/06/2012	Updated DC Electrical Characteristics: Fixed typo (Replaced mA with μA in "Units" column for I_{SB},I_{ZZ},I_{IX} and I_{OZ} parameters).	
*E	3671902	GVCH	07/24/2012	Updated DC Electrical Characteristics: Added V _{VCAP} parameter and its details. Added Note 8 and referred the same note in V _{VCAP} parameter. Referred Note 9 in V _{VCAP} parameter.	
*F	3762245	GVCH	10/01/2012	Updated Maximum Ratings: Removed "Ambient temperature with power applied" and its corresponding details. Added "Maximum junction temperature" and its corresponding details.	
*G	3845357	GVCH	12/18/2012	Updated Ordering Information: Updated part numbers (Added MPNs CY14E256Q1A-SXI, CY14E256Q1A-SXIT, CY14E256Q2A-SXI and CY14E256Q2A-SXIT).	



Document History Page (continued)

Rev.	ECN No.	Orig. of Change	Submission Date	Description of Change
*H	4188285	GVCH	11/11/2013	Updated Package Diagrams: spec 51-85066 – Changed revision from *E to *F. spec 51-85022 – Changed revision from *D to *E. Added watermark as "Not Recommended for New Designs". Updated to new template. Completing Sunset Review.
*	4567905	GVCH	11/12/2014	Updated Functional Description: Added "For a complete list of related documentation, click here." at the end Updated Ordering Information: Updated part numbers (Removed pruned MPNs CY14B256Q1A-SXIT, CY14B256Q1A-SXI, CY14E256Q1A-SXIT, CY14E256Q1A-SXI). Completing Sunset Review.
*J	6072136	GVCH	02/28/2018	Obsolete document. Completing Sunset Review.





Sales, Solutions, and Legal Information

Worldwide Sales and Design Support

Cypress maintains a worldwide network of offices, solution centers, manufacturer's representatives, and distributors. To find the office closest to you, visit us at Cypress Locations.

Products

Automotive Clocks & Buffers Interface

Memory
PSoC
Touch Sensing
USB Controllers

Wireless/RF

Lighting & Power Control

cypress.com/go/automotive cypress.com/go/clocks cypress.com/go/interface cypress.com/go/powerpsoc cypress.com/go/plc cypress.com/go/memory cypress.com/go/psoc cypress.com/go/touch cypress.com/go/USB cypress.com/go/wireless

PSoC® Solutions

psoc.cypress.com/solutions PSoC 1 | PSoC 3 | PSoC 4 | PSoC 5LP

Cypress Developer Community

Community | Forums | Blogs | Video | Training

Technical Support

cypress.com/go/support

© Cypress Semiconductor Corporation, 2010-2018. The information contained herein is subject to change without notice. Cypress Semiconductor Corporation assumes no responsibility for the use of any circuitry other than circuitry embodied in a Cypress product. Nor does it convey or imply any license under patent or other rights. Cypress products are not warranted nor intended to be used for medical, life support, life saving, critical control or safety applications, unless pursuant to an express written agreement with Cypress. Furthermore, Cypress does not authorize its products for use as critical components in life-support systems where a malfunction or failure may reasonably be expected to result in significant injury to the user. The inclusion of Cypress products in life-support systems application implies that the manufacturer assumes all risk of such use and in doing so indemnifies Cypress against all charges.

Any Source Code (software and/or firmware) is owned by Cypress Semiconductor Corporation (Cypress) and is protected by and subject to worldwide patent protection (United States and foreign), United States copyright laws and international treaty provisions. Cypress hereby grants to licensee a personal, non-exclusive, non-transferable license to copy, use, modify, create derivative works of, and compile the Cypress Source Code and derivative works for the sole purpose of creating custom software and or firmware in support of licensee product to be used only in conjunction with a Cypress integrated circuit as specified in the applicable agreement. Any reproduction, modification, translation, compilation, or representation of this Source Code except as specified above is prohibited without the express written permission of Cypress.

Disclaimer: CYPRESS MAKES NO WARRANTY OF ANY KIND, EXPRESS OR IMPLIED, WITH REGARD TO THIS MATERIAL, INCLUDING, BUT NOT LIMITED TO, THE IMPLIED WARRANTIES OF MERCHANTABILITY AND FITNESS FOR A PARTICULAR PURPOSE. Cypress reserves the right to make changes without further notice to the materials described herein. Cypress does not assume any liability arising out of the application or use of any product or circuit described herein. Cypress does not authorize its products for use as critical components in life-support systems where a malfunction or failure may reasonably be expected to result in significant injury to the user. The inclusion of Cypress' product in a life-support systems application implies that the manufacturer assumes all risk of such use and in doing so indemnifies Cypress against all charges.

Use may be limited by and subject to the applicable Cypress software license agreement.