GD CSSRM2.14

OSLON® Square

This most compact high-power LED (2 W class) allows dense clustering and simple circuit designs. Its extremely low thermal resistance helps to keep the efficiency remarkably high even when driven at high currents. High reliability. Long lifetime.







Applications

Architecture

Horticulture Lighting

Features:

- Package: SMD ceramic package with silicone lens
- Typ. Radiation: 120° (Lambertian emitter)
- Corrosion Robustness Class: 3B
- ESD: 8 kV acc. to ANSI/ESDA/JEDEC JS-001 (HBM, Class 3B)
- Radiant Flux: typ. 1507 mW @ 700mA; typ. 791 mW @ 350mA
- Radiant Efficiency: typ. 74 % @ 700mA; typ. 82 % @ 350mA
- Photosynthetic Photon Flux: typ. 5.69 µmol/s





Ordering Information		
Туре	Total radiant flux $^{1)}$ I _F = 700 mA $\Phi_{\rm E}$	Ordering Code
GD CSSRM2.14-ARAK-24-1	1300 1640 mW	Q65112A4742
GD CSSRM2.14-ARAK-24-1-L	1300 1640 mW	Q65113A2223
GD CSSRM2.14-ASAK-24-1-L	1400 1640 mW	Q65113A2362



Maximum Ratings			
Parameter	Symbol		Values
Operating Temperature	T _{op}	min. max.	-40 °C 120 °C
Storage Temperature	T _{stg}	min. max.	-40 °C 120 °C
Junction Temperature	T _j	max.	135 °C
Junction Temperature absolute*	Tj,abs	max.	150 °C
Forward current	I _F	min. max.	100 mA 2000 mA
Surge Current $t \le 10 \ \mu s; \ D = 0.005 \ \%; \ T_J = 25 \ ^{\circ}C$	I _{FS}	max.	2000 mA
Reverse voltage ²⁾	V_R		Not designed for reverse operation
ESD withstand voltage acc. to ANSI/ESDA/JEDEC JS-001 (HBM, Class 3B)	V_{ESD}		8 kV

 $^{^{**}}$ This is verified by testing 30 pieces. Pass criteria: No catastrophic failures allowed, luminous flux must be better than L70B50 after 1000 h.



Characteristics

 $I_F = 700 \text{ mA}; T_J = 25 \text{ }^{\circ}\text{C}$

Parameter	Symbol		Values
Peak Wavelength	$\lambda_{\sf peak}$	typ.	445 nm
Dominant Wavelength 3)	$\lambda_{\sf dom}$	min.	444 nm
$I_{\rm F} = 700 \text{mA}$	dom	typ.	450 nm
•		max.	457 nm
Spectral Bandwidth at 50% I _{rel,max}	Δλ	typ.	18 nm
Viewing angle at 50% I _v	2φ	typ.	120 °
Forward Voltage 4)	V_{F}	min.	2.80 V
$I_{\rm F} = 700 \text{mA}$		typ.	2.90 V
		max.	3.20 V
Reverse current 2)	I _R		Not designed for reverse operation
Electrical thermal resistance junction/solderpoint with efficiency $\eta_{\rm e}$ = 65 %	$R_{ ext{thJS elec.}}$	typ.	1.3 K / W



Brigh	ntness	Group	S					
Group	Total radiant flux 1)	Total radiant flux 1)	PPF *	PPF *	PPF/W*	BPF **	BPF **	BPF/W **
	$\begin{array}{l} \text{min.} \\ \boldsymbol{\varphi}_{\text{E}} \end{array}$	max. Φ _E	$\begin{array}{c} \text{min.} \\ \boldsymbol{\varphi_p} \end{array}$	\max_{Φ_p}	typ.	$\begin{array}{l} \text{min.} \\ \boldsymbol{\varphi}_{p,b} \end{array}$	$\max_{\Phi_{p,b}}$	typ.
AR	1300 mW	1400 mW	4.88 µmol/s	5.25 µmol/s	2.50 µmol/J	4.90 µmol/s	5.27 µmol/s	2.51 µmol/J
AS	1400 mW	1500 mW	5.25 µmol/s	5.63 µmol/s	2.68 µmol/J	5.27 μmol/s	5.65 µmol/s	2.69 µmol/J

 $5.63 \ \mu mol/s$ $5.82 \ \mu mol/s$ $2.82 \ \mu mol/J$ $5.65 \ \mu mol/s$ $5.84 \ \mu mol/s$ $2.83 \ \mu mol/J$

5.82 μmol/s 6.01 μmol/s 2.91 μmol/J 5.84 μmol/s 6.03 μmol/s 2.03 μmol/J

Note: [1] Includes wavelengths between 400 and 700 nm Note: [2] Includes wavelengths between 280 and 800 nm

1550 mW

1640

mW

Forward Voltage Groups

1500

1550

mW

mW

ΑJ

ΑK

Group	Forward Voltage ⁴⁾ I _F = 700 mA	Forward Voltage 4) I _F = 700 mA	
	min. V _F	max. V _F	
L1	2.80 V	2.90 V	
L2	2.90 V	3.00 V	
M1	3.00 V	3.10 V	
M2	3.10 V	3.20 V	

Wavelength Groups

Group	Dominant Wavelength 3)	Dominant Wavelength 3)
	$I_{\rm F} = 700 \text{mA}$	$I_F = 700 \text{ mA}$
	min.	max.
	λ_{dom}	λ_{dom}
2	444 nm	449 nm
3	449 nm	453 nm
4	453 nm	457 nm



Group Name on Label


Example: AJ-2-L1

Brightness	Wavelength	Forward Voltage
AJ	2	L1




Relative Spectral Emission 5)

 $I_{rel} = f(\lambda); I_F = 700 \text{ mA}; T_J = 25 ^{\circ}\text{C}$




Radiation Characteristics 5)

 $I_{rel} = f(\phi); T_J = 25 °C$




Forward current 5), 6)

$$I_F = f(V_F); T_J = 25 \, ^{\circ}C$$




Relative Radiant Power 5), 6)

$$\Phi_{\rm E}/\Phi_{\rm E}(700~{\rm mA})$$
 = f(I_F); T_J = 25 °C




Dominant Wavelength 5)

$$\Delta\lambda_{dom} = f(I_F); T_J = 25 \text{ }^{\circ}\text{C}$$




Forward Voltage 5)

$$\Delta V_{_F} = V_{_F} - V_{_F} (25 \ ^{\circ}C) = f(T_{_j}); \ I_{_F} = 700 \ \text{mA}$$




Relative Radiant Power 5)

$$\Phi_{\rm E}/\Phi_{\rm E}(25~^{\circ}{\rm C})$$
 = f(T_i); I_F = 700 mA




Dominant Wavelength 5)

$$\Delta \lambda_{dom} = \lambda_{dom} - \lambda_{dom} (25~^{\circ}\text{C}) = f(T_j);~ I_F = 700~\text{mA}$$




Max. Permissible Forward Current


 $I_F = f(T)$






Dimensional Drawing 7)







General tolerance ±0.1 Lead finish Au

C67062-A0212-A2-01

Further Information:

Approximate Weight: 29.0 mg

Package marking: Cathode

Corrosion test: Class: 3B

Test condition: 40°C / 90 % RH / 15 ppm H₂S / 14 days (stricter than IEC


60068-2-43)

The device is protected by ESD device which is connected in parallel to the **ESD** advice:

Chip.



Recommended Solder Pad 7)




For superior solder joint connectivity results we recommend soldering under standard nitrogen atmosphere. Further information can be found in our Application Note: "Handling and Processing Details for Ceramic LEDs".



Reflow Soldering Profile

Product complies to MSL Level 2 acc. to JEDEC J-STD-020E




Profile Feature	Symbol	abol Pb-Free (SnAgCu) Assembly			Unit
		Minimum	Recommendation	Maximum	
Ramp-up rate to preheat*)			2	3	K/s
25 °C to 150 °C					
Time t _s	t_s	60	100	120	S
T_{Smin} to T_{Smax}					
Ramp-up rate to peak*)			2	3	K/s
T_{Smax} to T_{P}					
Liquidus temperature	T_L		217		°C
Time above liquidus temperature	$t_{\scriptscriptstyle \perp}$		80	100	S
Peak temperature	T_{P}		245	260	°C
Time within 5 °C of the specified peak	t _P	10	20	30	S
temperature T _P - 5 K					
Ramp-down rate*			3	6	K/s
T _P to 100 °C					
Time				480	S
25 °C to T _P					

All temperatures refer to the center of the package, measured on the top of the component




^{*} slope calculation DT/Dt: Dt max. 5 s; fulfillment for the whole T-range

Taping 7)



C67062-A0212-B11-01

Tape and Reel 8)




Reel Dimensions

Α	W	N_{\min}	W ₁	$W_{2 max}$	Pieces per PU
180 mm	12 + 0.3 / - 0.1 mm	60 mm	12.4 + 2 mm	18.4 mm	600
330 mm	12 + 0.3 / - 0.1 mm	60 mm	12.4 + 2 mm	18.4 mm	3000

Barcode-Product-Label (BPL)



Dry Packing Process and Materials 7)



Moisture-sensitive product is packed in a dry bag containing desiccant and a humidity card according JEDEC-STD-033.



Notes

The evaluation of eye safety occurs according to the standard IEC 62471:2006 (photo biological safety of lamps and lamp systems). Within the risk grouping system of this IEC standard, the device specified in this data sheet falls into the class moderate risk (exposure time 0.25 s). Under real circumstances (for exposure time, conditions of the eye pupils, observation distance), it is assumed that no endangerment to the eye exists from these devices. As a matter of principle, however, it should be mentioned that intense light sources have a high secondary exposure potential due to their blinding effect. When looking at bright light sources (e.g. headlights), temporary reduction in visual acuity and afterimages can occur, leading to irritation, annoyance, visual impairment, and even accidents, depending on the situation.

Subcomponents of this device contain, in addition to other substances, metal filled materials including silver. Metal filled materials can be affected by environments that contain traces of aggressive substances. Therefore, we recommend that customers minimize device exposure to aggressive substances during storage, production, and use. Devices that showed visible discoloration when tested using the described tests above did show no performance deviations within failure limits during the stated test duration. Respective failure limits are described in the IEC60810.

This device is designed for specific/recommended applications only. Please consult OSRAM Opto Semiconductors Sales Staff in advance for detailed information on other non-recommended applications (e.g. automotive).

Change management for this component is aligned with the requirements of the lighting market.

For further application related information please visit www.osram-os.com/appnotes



Disclaimer

Attention please!

The information describes the type of component and shall not be considered as assured characteristics. Terms of delivery and rights to change design reserved. Due to technical requirements components may contain dangerous substances.

For information on the types in question please contact our Sales Organization.

If printed or downloaded, please find the latest version on the OSRAM OS website.

Packing

Please use the recycling operators known to you. We can also help you – get in touch with your nearest sales office. By agreement we will take packing material back, if it is sorted. You must bear the costs of transport. For packing material that is returned to us unsorted or which we are not obliged to accept, we shall have to invoice you for any costs incurred.

Product and functional safety devices/applications or medical devices/applications

OSRAM OS components are not developed, constructed or tested for the application as safety relevant component or for the application in medical devices.

OSRAM OS products are not qualified at module and system level for such application.

In case buyer – or customer supplied by buyer – considers using OSRAM OS components in product safety devices/applications or medical devices/applications, buyer and/or customer has to inform the local sales partner of OSRAM OS immediately and OSRAM OS and buyer and /or customer will analyze and coordinate the customer-specific request between OSRAM OS and buyer and/or customer.



Glossary

- Brightness: Brightness values are measured during a current pulse of typically 10 ms, with a tolerance of +/- 7%.
- Reverse Operation: Not designed for reverse operation. Continuous reverse operation can cause migration and damage of the device.
- Wavelength: The wavelength is measured at a current pulse of typically 10 ms, with a tolerance of ± 0.5 nm.
- Forward Voltage: The Forward voltage is measured during a current pulse duration of typically 1 ms with a tolerance of ± 0.05 V.
- Typical Values: Due to the special conditions of the manufacturing processes of semiconductor devices, the typical data or calculated correlations of technical parameters can only reflect statistical figures. These do not necessarily correspond to the actual parameters of each single product, which could differ from the typical data and calculated correlations or the typical characteristic line. If requested, e.g. because of technical improvements, these typ. data will be changed without any further notice.
- 6) Characteristic curve: In the range where the line of the graph is broken, you must expect higher differences between single devices within one packing unit.
- Tolerance of Measure: Unless otherwise noted in drawing, tolerances are specified with ±0.1 and dimensions are specified in mm.
- ⁸⁾ **Tape and Reel:** All dimensions and tolerances are specified acc. IEC 60286-3 and specified in mm.



GD CSSRM2.14

	Revision History					
Version	Date	Change				
1.1	2019-09-24	New Layout Schematic Transportation Box Dimensions of Transportation Box				
1.2	2020-07-02	Ordering Information Brightness Groups				
1.3	2020-10-14	Ordering Information Brightness Groups Reel Dimensions				
1.3	2020-11-25	Ordering Information				



Leibnizstraße 4, D-93055 Regensburg www.osram-os.com © All Rights Reserved.

Published by OSRAM Opto Semiconductors GmbH EU RoHS and China RoHS compliant product

此产品符合欧盟 RoHS 指令的要求; 按照中国的相关法规和标准,不含有毒有害物质或元素。

