


# **Evaluation Board User's Guide**

ADC10DV200, 10-Bit, 200 Msps A/D Converter ADC11DV200, 11-Bit, 200 Msps A/D Converter



© 2009 National Semiconductor Corporation.

# **Table of Contents**

| 1.0 Introduction  | . 3  |
|---|------|
| 2.0 Board Assembly  | . 3  |
| 3.0 Quick Start.  | . 4  |
| 4.0 Functional Description  | . 4  |
| 4.1 Analog Input  | . 4  |
| 4.2 ADC reference circuitry   | . 5  |
| 4.3 ADC clock circuit   | . 5  |
| 4.4 Digital Data Output   | . 5  |
| 4.5 Data Format/ Duty Cycle Stabilizer                              |      |
| 4.6 Power Supply Connections  | . 5  |
| 5.0 Installing the ADC10DV200 Evaluation Board                      | . 5  |
| 6.0 Hardware Schematic  | . 6  |
| 7.0 Evaluation Board Layout   | . 12 |
| 8.0 Evaluation Board Bill of Materials                              | . 15 |
| A1.0 Operating in the Computer Mode                                 | . 17 |
| A2.0 Summary Tables of Test Points, Connectors, and Jumper Settings |      |
| A2.1 Test Points  |      |
| A2.2 Connectors   | . 17 |
| A2.3 Jumper settings  |      |
| A2.4 Clock Circuit Solder Jumper settings                           |      |

# 1.0 Introduction

This Evaluation Board may be used to evaluate the ADC10DV200, or ADC11DV200. The ADC is one of a family of 10 and 11 bit converters that provides data at rates of up to 200MHz. Further reference in this manual to the ADC10DV200 is meant to also include the other listed parts unless otherwise specified

The evaluation board is designed to be used with the WaveVision5™ Data Capture Board which is connected to a personal computer through a USB port and running WaveVision5™ software, operating under Microsoft Windows. The software can perform an FFT on the captured data upon command and, in addition to a

frequency domain plot, shows dynamic performance in the form of SNR, SINAD, THD and SFDR. The latest WaveVision hardware and software is available through the National Semiconductor website:

http://www.national.com/store/view\_item/index.html?nsid= WAVEVSN+BRD+5.1

# 2.0 Board Assembly

The ADC10DV200 Evaluation Board comes preassembled. Refer to the Bill of Materials in *Section 8* for a description of components, to *Figure 1* for major component placement and to *Section 6* for the Evaluation Board schematic.




Figure 1. Major Component and Jumper Locations




Figure 2. Test Set up

### 3.0 Quick Start

Refer to Figure 1 for locations of jumpers, test points and major components. Refer to Figure 2 for the test set up. The board is configured by default to use a external clock source and internal reference. Refer to Section 4.0 and the Appendix for more information on jumper settings. The input network of this board is configured for input frequencies greater than 70MHz. Refer to Section 4.1 for more information about input networks.

You must have version 5.0 or later of the WaveVision™ software to properly test this board. You can download the latest version from:

http://www.national.com/analog/adc/wavevision5

- Apply power to the WaveVision5<sup>™</sup> board and connect it to the computer using a USB cable. See the WaveVision5<sup>™</sup> Board Manual for operation of that board. Connect the evaluation board to the WaveVision<sup>™</sup> Digital Interface Board.
- Connect a clean +5V power supply to pin 2 of Power Connector JR507. Pin 1 is ground.
- 3. Connect a signal from a 50-Ohm source to connector J301 or J302. Be sure to use a bandpass filter before the Evaluation Board.
- Adjust the input signal amplitude as needed to ensure that the signal does not over-range by examinining a histogram of the output data with the WaveVision5™ software.

### 4.0 Functional Description

The ADC10DV200 Evaluation Board schematic is shown in *Section 6*. A list of test points and jumper settings can be found in the Appendix.

### 4.1 Analog Input

To obtain the best distortion results the analog input network must be optimized for the signal frequency being applied. The ADC10DV200 Evaluation Board comes configured as seen in *Figure 3*.




Figure 3. Analog Input Network for  $F_{IN} > 70MHz$ 

The input network is intended to accept a low-noise sine wave and will perform well over a wide input frequency range. To accurately evaluate the dynamic performance of this converter, the input test signal will have to be passed through a high-quality bandpass filter.

Input signals can also be amplified using an onboard LMH6517 DVGA (U601). To use the DVGA, some components must be installed and some removed. The following components must be installed: R651-R656. The following components must be removed: R302, R303, R309, and R310. Then connect signals from a 50-Ohm source to connectors J601 and J607.

#### 4.2 ADC reference circuitry

The ADC10DV200 can use an internal or external voltage reference. The internal reference is selectable between a 0.75V or 0.5V reference. External references can be set from 0.2V to 1.4V. This Evaluation Board is configured to use the internal 0.75V reference.

#### 4.3 ADC clock circuit

Components can be installed or removed to select the path of the clock to the ADC. While not as convenient as pin-type jumpers, these introduce less distortion into the clock signal.

Care must be taken to provide a high quality low jitter clock source. A single ended input clock can be buffered by U203 (NC7SV125) and applied to the ADC's clock input pin. Or U203 can be bypassed and the input clock pin driven directly.

A differential clock can also be applied to the ADC's clock input pins through U201 (ETC-1-13).

Refer to Appendix A to configure the clock for your application. The Evaluation Board is configured by default to use a single ended clock to drive the input pins directly.

#### 4.4 Digital Data Output

The LVDS digital output data is available for probing at test points TP601 through TP624. The signals are also available at the WaveVision™ (WV5) connector J602.

### 4.5 Data Format/ Duty Cycle Stabilizer

Output data format and the duty cycle stabilizer (DCS) are controlled by jumper J401.

Shorting pins 1-2 of J401 sets the output format to offset binary with DCS On. This is the default setting.

Shorting pins 3-4 of J401 sets the output format to 2's complement with DCS Off.

Shorting pins 5-6 of J401 sets the output format to offset binary with DCS Off.

Shorting pins 7-8 of J401 sets the output format to 2's complement with DCS On.

#### 4.6 Power Supply Connections

Power to this board is supplied through power connector J507. The only supply needed is +5V at pin 2 plus ground at pin 1.

Voltage and current requirements for the ADC10DV200 Evaluation Board are:


+5.0V at 500 mA


### 5.0 Installing the ADC10DV200 Evaluation Board


The evaluation board requires power supplies as described in Section 4.6. An appropriate signal source


should be connected to the Signal Input SMA connectors J301 or J302. When evaluating dynamic performance, an appropriate signal generator (such as the HP8644B or the R&S SME-03) with 50 Ohm source impedance should be connected to the Analog Input connector through an appropriate bandpass filter as even the best signal generator available can not produce a signal pure enough to evaluate the dynamic performance of an ADC.


If this board is used in conjunction with the WaveVision5<sup>TM</sup> Data Capture Board and WaveVision5<sup>TM</sup> software, a USB must be connected between the Data Capture Board Board and the host. See the WaveVision5<sup>TM</sup> Data Capture Board manual for details.

















# 7.0 Evaluation Board Layout




Layer 1 : Component Side




Layer 2 : Ground




Layer 3 : Ground



Layer 4 : Power



Layer 5 : Ground



Layer 6 : Circuit Side

# **8.0 Evaluation Board Bill of Materials**

| Item | Qty | Reference                                    | Part Part        | Part Number  | Vendor   |
|------|-----|--|------------------|--------------|----------|
|      |     |  |                  |              |          |
| 1    | 15  | C201,C220,                                   | .1uF             | PCC1762CT    | Digi-Key |
|      |     | C301,C302,C313,C314,                         |                  |              |          |
|      |     | C315,C316,C504,C509,C514,                    |                  |              |          |
| 3    | 8   | C518,C547,C549,C551<br>C305,C309,C311,       | .1uF             | 490-1318-1   | Digi-Key |
| J    | O   | C303,C304,C311,<br>C312,C318,C322,C324,C325, | . Tui            | 490-1310-1   | Digi-key |
| 4    | 10  | C218,C502,C505,C507,C510,                    | .01uF            | PCC1784CT    | Digi-Key |
| ·    |     | C512,C515,C548,C550,C552                     |                  |              | - 9 ,    |
| 5    | 1   | C219   | 1uF              | PCC2224CT    | Digi-Key |
| 6    | 2   | C307,C320                                    | 27pF             | PCC270CQCT   | Digi-Key |
| 7    | 2   | C310,C323                                    | .1uF             | PCC2336CT    | Digi-Key |
| 8    | 4   | C401,C402,C403,C627                          | .1uF             | PCC1828CT    | Digi-Key |
| 9    | 3   | C501,C506,C511                               | 4.7uF            | PCC1842CT    | Digi-Key |
| 10   | 6   | C503,C508,C513,C544,C545,                    | 10uF             | PCC1894CT    | Digi-Key |
|      |     | C546   |                  |              |          |
| 11   | 1   | C516   | 22uF             | 399-3717-1   | Digi-Key |
| 12   | 1   | C517   | 10uF             | 399-3705-1   | Digi-Key |
| 13   | 9   | C520,C522,C524,C526,C528,                    | .1uF             | PCC2146CT    | Digi-Key |
|      |     | C530,C532,C534,C536                          |                  |              |          |
| 14   | 10  | C521,C523,C525,C527,C529,                    | .01uF            | PCC2270CT    | Digi-Key |
|      |     | C531,C533,C535,C537,C538                     |                  |              |          |
| 18   | 3   | D501,D502,D503                               | BAT54            | BAT54-FDICT  | Digi-Key |
| 19   | 1   | JP204  | HEADER 2         | N/A          |          |
| 20   | 1   | JP401  | V_PDA            | S1011E-2     |          |
| 21   | 1   | JP402  | V_PDB            | S1011E-2     |          |
| 22   | 1   | JR507  | +5V              | 277-1150     | Digi-Key |
| 23   | 1   | J101   | VREF             | S2011E-3     |          |
| 24   | 1   | J201   | EXT. CLK         | ARFX1231     | Digi-Key |
| 25   | 1   | J301   | ANALOG IN B      | ARFX1231     |          |
| 26   | 1   | J302   | ANALOG IN A      | ARFX1231     |          |
| 27   | 1   | J401   | DF/DCS           | S2011E-4     |          |
| 29   | 1   | J602   | CONN 60 PIN HMZD | 6469028-1    | Digi-Key |
| 31   | 4   | L501,L502,L503,L504                          | 10UH             | 490-1055-1   | Digi-Key |
| 34   | 1   | R101   | 3.3K             | 311-3.3KARCT | Digi-Key |
| 35   | 1   | R103   | 20K              | 3296y-203LF  | Digi-Key |
| 37   | 1   | R106   | 10K              | 311-10KGRCT  | Digi-Key |
| 38   | 1   | R201   | 49.9             | P49.9HCT     | Digi-Key |
| 39   | 2   | R202,R203                                    | 1K               | P1.00KHCT    | Digi-Key |
| 40   | 6   | R218,R219,R304,R311,R313,                    | 24.9             | P24.9LCT     | Digi-Key |
|      |     | R316   |                  |              |          |
| 41   | 2   | R220,R221                                    | 10K              | P10.0KHCT    | Digi-Key |
| 42   | 2   | R224,R225                                    | 0                | 311-0.0GRCT  | Digi-Key |
| 43   | 4   | R302,R303,R309,R310                          | 30               | 311-30JRCT   | Digi-Key |
| 44   | 4   | R305,R307,R312,R314                          | 0                | 311-0.0JRCT  | Digi-Key |
| 45   | 2   | R306,R315                                    | 49.9             | 311-49.9HRCT | Digi-Key |

| 46  | 3  | R401,R404,R405            | 10K                           | 311-10KARCT                         | Digi-Key      |
|-----|----|---------------------------|-------------------------------|-------------------------------------|---------------|
| 47  | 2  | R402,R403                 | 5.1K                          | 311-5.1KARCT                        | Digi-Key      |
|     |    |                           |                               |                                     |               |
| 70  | 6  | TP501,TP502,TP503,TP504,  | GND                           | 5002K                               | Digi-Key      |
|     |    | TP505,TP506               |                               |                                     |               |
| 71  | 1  | TP507                     | VA                            | 5002K                               | Digi-Key      |
| 72  | 1  | TP508                     | VD                            | 5002K                               | Digi-Key      |
| 73  | 1  | TP509                     | VCLK                          | 5002K                               | Digi-Key      |
| 74  | 1  | TP510                     | VDR                           | 5002K                               | Digi-Key      |
| 7 - |    | 11 310                    | VDIC                          | 300ZK                               | bigi Key      |
| 100 | 4  | T301,T305,T302,T306       | ETC1-1-13                     | ETC1-1-13                           | Richardson    |
| 100 | 4  | 1301,1303,1302,1300       | LIGI-1-13                     | E1G1-1-13                           | Richardson    |
|     |    |                           |                               |                                     |               |
| 102 | 1  | U1                        | ADC10DV200 (or<br>ADC11DV200) | ADC10DV200CISQ or<br>ADC11DV200CISQ |               |
|     | 1  |                           | ,                             |                                     | Mouser        |
| 104 | 1  | U203                      | NC7SV125                      | NC7SV125P5X                         | Mouser        |
| 105 | 3  | U501,U502,U503            | LP2989LV-1.8                  | LP2989AIM-1.8                       | Digi-Keys     |
| 107 | 1  | U606                      | 24C02/SO8                     | 511-M24C02-WMN6P                    | Mouser        |
|     |    | DO NOT POPULATE           |                               |                                     |               |
| 100 | 1  | U201                      | ETC1-1-13                     | ETC1-1-13                           | Richardson    |
| 101 | 2  | T307,T308                 | MABACT0040                    | MABACT0040                          | Richardson    |
| 36  | 3  | R105,R301,R308            | DNP                           |                                     |               |
| 42  | 2  | R222,R223                 | 0                             | 311-0.0GRCT                         | Digi-Key      |
| 2   | 3  | C213,C214,C215            | DNP                           |                                     |               |
| 3   | 2  | C216,C217                 | .1uF                          | 490-1318-1                          | Digi-Key      |
| 1   | 4  | C210,C211,C212,C221       | .1uF                          | PCC1762CT                           | Digi-Key      |
| 106 | 1  | U601                      | LMH6517                       | LMH6517SQ                           | National      |
| 28  | 1  | J601                      | INPUT A                       | WM5534                              | Digi-Key      |
| 30  | 1  | J607                      | INPUT B                       | WM5534                              | Digi-Key      |
| 48  | 4  | R601,R602,R640,R642       | DNP                           |                                     |               |
| 56  | 2  | SW1,SW2                   | SW DIP-8                      | GH7176                              | Digi-Key      |
| 99  | 2  | T1,T2                     | TCM4-19+                      | TCM4-19+                            | Mini-Circuits |
| 50  | 18 | R611,R612,R613,R614,R615, | 20K                           | P20.0KLCT                           | Digi-Key      |
|     |    | R616,R617,R618,R627,R628, |                               |                                     | 3 ,           |
|     |    | R629,R630,R631,R632,R633, |                               |                                     |               |
|     |    | R634,R637,R638            |                               |                                     |               |
| 49  | 16 | R603,R604,R605,R606,R607, | 10K                           | 311-10KJRCT                         | Digi-Key      |
| 17  | 10 | R608,R609,R610,R619,R620, | TOIL                          | orr rolland.                        | Digi Koj      |
|     |    | R621,R622,R623,R624,R625, |                               |                                     |               |
|     |    | R626                      |                               |                                     |               |
| E1  | 2  | R635,R636                 | 10K                           | 211 10 OVI CT                       | Digi Koy      |
| 51  | 2  |                           |                               | 311-10.0KLCT                        | Digi-Key      |
| 32  | 4  | L601,L602,L604,L605       | 129nH                         | 495-3433-1                          | Digi-Key      |
| 33  | 2  | L603,L606                 | 1nH                           | 044.0.0.IDOT                        | D: 11/        |
| 44  | 4  | R653,R654,R655,R656       | 0                             | 311-0.0JRCT                         | Digi-Key      |
| 52  | 2  | R639,R641                 | 0                             | 311-0.0JRCT                         | Digi-Key      |
| 53  | 4  | R643,R644,R645,R646       | 49.9                          | 311-49.9LCT                         | Digi-Key      |
| 54  | 4  | R647,R648,R649,R650       | 100                           | 311-100JCT                          | Digi-Key      |
| 55  | 2  | R651,R652                 | 10                            | 311-10JRCT                          | Digi-Key      |
| 3   | 10 | C601,C602,C603,C604,C605, | .1uF                          | 490-1318-1                          | Digi-Key      |
|     |    | C606,C607,C608,C609,C611  |                               |                                     |               |
| 15  | 8  | C610,C612,C613,C614,C615, | 0.01uF                        | PCC103BQCT                          | Digi-Key      |
|     |    | C616,C623,C625            |                               |                                     |               |
| 16  | 2  | C617,C618                 | 15pF                          | PCC150CQCT                          | Digi-Key      |
| 17  | 2  | C624,C626                 | 1uF                           | PCC2364CT                           | Digi-Key      |
| 6   | 4  | C619,C620,C621,C622       | 27pF                          | PCC270CQCT                          | Digi-Key      |
|     |    |                           |                               |                                     |               |

# **APPENDIX**

### A1.0 Operating in the Computer Mode

The ADC10DV200 Evaluation Board is compatible with the WaveVision5™ Data Capture Board and WaveVision5™ software. You can download the latest version from: <a href="http://www.national.com/analog/adc/wavevision5">http://www.national.com/analog/adc/wavevision5</a>

When connected to the WaveVision5™ Board, data capture is easily controlled from a personal computer operating in the Windows environment. The data samples that are captured can be observed on the PC video monitor in the time and frequency domains. The FFT analysis of the captured data yields insight into system noise and distortion sources and estimates of ADC dynamic performance such as SINAD, SNR and THD.

# A2.0 Summary Tables of Test Points, Connectors, and Jumper Settings

#### **A2.1 Test Points**

### Test Points on the ADC10DV200 Evaluation Board

| Voltage Signal Name | Measure at | Nominal Voltage (V) | Voltage Limits (V) |
|---------------------|------------|---------------------|--------------------|
| VA                  | TP507      | 1.8                 | 1.7 to 1.9         |
| VD                  | TP508      | 1.8                 | 1.7 to 1.9         |
| VDR                 | TP510      | 1.8                 | 1.7 to 1.9         |
| VCLK                | TP509      | 1.8                 | 1.7 to 1.9         |

#### **A2.2 Connectors**

# JR507 Connector - Power Supply Connections

| 1 | GND | Power Supply Ground |
|---|-----|---------------------|
| 2 | +5V | +5V Power Supply    |

### A2.3 Jumper settings

Note: Default settings are in bold

#### JP401: Power Down Channel A

| Connect 1-2 | Channel A is in power down mode  |
|-------------|----------------------------------|
| 1-2 OPEN    | Channel A is in normal operation |

# JP402: Power Down Channel B

| Connect 1-2 | Channel B is in power down mode  |  |
|-------------|----------------------------------|--|
| 1-2 OPEN    | Channel B is in normal operation |  |

#### J401: Output Data Format and Duty Cycle Stabilizer

| Connect 1-2 | Output format is offset binary, DCS is On   |
|-------------|---|
| Connect 3-4 | Output format is 2's complement, DCS is Off |
| Connect 5-6 | Output format is offset binary, DCS is Off  |
| Connect 7-8 | Output format is 2's complement, DCS is On  |

# **A2.4 Clock Circuit Solder Jumper settings**

Components can be installed or removed to select the path of the clock to the ADC. While not as convenient as pin-type jumpers, these introduce less distortion into the clock signal.

| Termination A: Differential Sinusoid | Install C210, C216, and C217                  |  |
|--------------------------------------|---|--|
|                                      | Remove R223, R224, R225, and JP204            |  |
| Termination B: Single Ended Sinusoid | Install R222 and R223                         |  |
|                                      | Remove C210, C216, C217, R224, R225 and JP204 |  |
| Termination C: Single Ended Square   | Install R223, R224, R225, and JP204           |  |
|                                      | Remove C210, C216, C217, and R222             |  |

BY USING THIS PRODUCT, YOU ARE AGREEING TO BE BOUND BY THE TERMS AND CONDITIONS OF NATIONAL SEMICONDUCTOR'S END USER LICENSE AGREEMENT. DO NOT USE THIS PRODUCT UNTIL YOU HAVE READ AND AGREED TO THE TERMS AND CONDITIONS OF THAT AGREEMENT. IF YOU DO NOT AGREE WITH THEM, CONTACT THE VENDOR WITHIN TEN (10) DAYS OF RECEIPT FOR INSTRUCTIONS ON RETURN OF THE UNUSED PRODUCT FOR A REFUND OF THE PURCHASE PRICE PAID, IF ANY.

The ADC10DV200 Evaluation Boards are intended for product evaluation purposes only and are not intended for resale to end consumers, is not authorized for such use and is not designed for compliance with European EMC Directive 89/336/EEC, or for compliance with any other electromagnetic compatibility requirements.

National Semiconductor Corporation does not assume any responsibility for use of any circuitry or software supplied or described. No circuit patent licenses are implied.

### LIFE SUPPORT POLICY

NATIONAL'S PRODUCTS ARE NOT AUTHORIZED FOR USE AS CRITICAL COMPONENTS IN LIFE SUPPORT DEVICES OR SYSTEMS WITHOUT THE EXPRESS WRITTEN APPROVAL OF THE PRESIDENT OF NATIONAL SEMICONDUCTOR CORPORATION. As used herein:

- Life support devices or systems are devices or systems which, (a) are intended for surgical implant into the body, or (b) support or sustain life, and whose failure to perform, when properly used in accordance with instructions for use provided in the labeling, can be reasonably expected to result in a significant injury to the user.
- A critical component is any component in a life support device or system whose failure to perform can be reasonably expected to cause the failure of the life support device or system, or to affect its safety or effectiveness.

National Semiconductor Corporation Americas

Tel: 1-800-272-9959 Fax: 1-800-737-7018 Email: support@nsc.com National Semiconductor Europe Fax: +49 (0) 1 80-530 85 86 Email: europe.support@nsc.com Deutsch Tel: +49 (0) 699508 6208

English Tel: +49 (0) 870 24 0 2171 Français Tel: +49 (0) 141 91 8790 National Semiconductor Asia Pacific Customer Response Group Tel: 65-2544466

Fax: 65-2504466 Email:sea.support@nsc.com National Semiconductor Japan Ltd.

Tel: 81-3-5639-7560 Fax: 81-3-5639-7507

#### www.national.com

National does not assume any responsibility for any circuitry described, no circuit patent licenses are implied and National reserves the right at any time without notice to change said circuitry and specifications.

#### IMPORTANT NOTICE

Texas Instruments Incorporated and its subsidiaries (TI) reserve the right to make corrections, modifications, enhancements, improvements, and other changes to its products and services at any time and to discontinue any product or service without notice. Customers should obtain the latest relevant information before placing orders and should verify that such information is current and complete. All products are sold subject to TI's terms and conditions of sale supplied at the time of order acknowledgment.

TI warrants performance of its hardware products to the specifications applicable at the time of sale in accordance with TI's standard warranty. Testing and other quality control techniques are used to the extent TI deems necessary to support this warranty. Except where mandated by government requirements, testing of all parameters of each product is not necessarily performed.

TI assumes no liability for applications assistance or customer product design. Customers are responsible for their products and applications using TI components. To minimize the risks associated with customer products and applications, customers should provide adequate design and operating safeguards.

TI does not warrant or represent that any license, either express or implied, is granted under any TI patent right, copyright, mask work right, or other TI intellectual property right relating to any combination, machine, or process in which TI products or services are used. Information published by TI regarding third-party products or services does not constitute a license from TI to use such products or services or a warranty or endorsement thereof. Use of such information may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

Reproduction of TI information in TI data books or data sheets is permissible only if reproduction is without alteration and is accompanied by all associated warranties, conditions, limitations, and notices. Reproduction of this information with alteration is an unfair and deceptive business practice. TI is not responsible or liable for such altered documentation. Information of third parties may be subject to additional restrictions.

Resale of TI products or services with statements different from or beyond the parameters stated by TI for that product or service voids all express and any implied warranties for the associated TI product or service and is an unfair and deceptive business practice. TI is not responsible or liable for any such statements.

TI products are not authorized for use in safety-critical applications (such as life support) where a failure of the TI product would reasonably be expected to cause severe personal injury or death, unless officers of the parties have executed an agreement specifically governing such use. Buyers represent that they have all necessary expertise in the safety and regulatory ramifications of their applications, and acknowledge and agree that they are solely responsible for all legal, regulatory and safety-related requirements concerning their products and any use of TI products in such safety-critical applications, notwithstanding any applications-related information or support that may be provided by TI. Further, Buyers must fully indemnify TI and its representatives against any damages arising out of the use of TI products in such safety-critical applications.

TI products are neither designed nor intended for use in military/aerospace applications or environments unless the TI products are specifically designated by TI as military-grade or "enhanced plastic." Only products designated by TI as military-grade meet military specifications. Buyers acknowledge and agree that any such use of TI products which TI has not designated as military-grade is solely at the Buyer's risk, and that they are solely responsible for compliance with all legal and regulatory requirements in connection with such use.

**Applications** 

TI products are neither designed nor intended for use in automotive applications or environments unless the specific TI products are designated by TI as compliant with ISO/TS 16949 requirements. Buyers acknowledge and agree that, if they use any non-designated products in automotive applications, TI will not be responsible for any failure to meet such requirements.

Following are URLs where you can obtain information on other Texas Instruments products and application solutions:

**Products** 

Wireless Connectivity

| Audio                  | www.ti.com/audio       | Automotive and Transportation | www.ti.com/automotive             |
|------------------------|------------------------|-------------------------------|-----------------------------------|
| Amplifiers             | amplifier.ti.com       | Communications and Telecom    | www.ti.com/communications         |
| Data Converters        | dataconverter.ti.com   | Computers and Peripherals     | www.ti.com/computers              |
| DLP® Products          | www.dlp.com            | Consumer Electronics          | www.ti.com/consumer-apps          |
| DSP                    | dsp.ti.com             | Energy and Lighting           | www.ti.com/energy                 |
| Clocks and Timers      | www.ti.com/clocks      | Industrial                    | www.ti.com/industrial             |
| Interface              | interface.ti.com       | Medical                       | www.ti.com/medical                |
| Logic                  | logic.ti.com           | Security                      | www.ti.com/security               |
| Power Mgmt             | power.ti.com           | Space, Avionics and Defense   | www.ti.com/space-avionics-defense |
| Microcontrollers       | microcontroller.ti.com | Video and Imaging             | www.ti.com/video                  |
| RFID                   | www.ti-rfid.com        |                               |                                   |
| OMAP Mobile Processors | www.ti.com/omap        |                               |                                   |

TI E2E Community Home Page

www.ti.com/wirelessconnectivity

e2e.ti.com