

SST-10-IRD-810nm

Dual Junction Surface Mount Series

Low Thermal Resistance Infrared LED




Table of Contents

| Technology Overview 2 |
|--|
| Product Binning3 |
| Ordering Information3 |
| Optical and Electrical Characteristics |
| Mechanical Dimensions 8 |
| Tape and Reel 10 |
| Reel Information 12 |
| Shipping information 13 |
| Soldering14 |
| Precautions 15 |
| Revision History16 |

Features

- High Power Infrared LED with typical 810nm centroid wavelength
- High thermal conductivity substrate
- 90 and 130-degree viewing angle
- Operation at up to 1.5A CW and 5A pulse
- Corrosion Robustness Class: 3B
- Built-in ESD protection
- Low Thermal Resistance
- Suitable for all SMT Assembly Methods
- RoHS and REACh compliant

Applications

- Surveillance Systems / CCTV
- Iris and Face Recognition
- License Plate Scanning
- Automotive Sensing
- Machine Vision
- Night Vision





Technology Overview

Luminus SST-10-IRD-810nm LEDs benefit from innovations in device technology, chip packaging and thermal management. This suite of technologies give engineers and system designers the freedom to develop solutions both high in power and efficiency.

Reliability

Luminus SST-10-IRD-810nm LEDs have passed a rigorous suite of environmental and mechanical stress tests, including HTOL, temperature cycling, humidity and corrosion resistance. They are fully qualified for use in a wide range of high performance and high efficacy applications.

REACh & RoHS Compliance

The Luminus SST-10-IRD-810nm LED is compliant to the Restriction of Hazardous Substances Directive or RoHS. The restricted materials including lead, mercury cadmium hexavalent chromium, polybrominated biphenyls (PBB) and polybrominated diphenyl ether (PBDE) are not used.

Understanding Luminus SST-10-IRD-810nm LED Test Specifications

Every Luminus LED is fully tested to ensure it meets the high quality standards customers have come to expect from Luminus products.

Testing Temperature

Luminus SST-10-IRD-810nm LEDs are tested and binned at 25°C junction temperature. Temperature curves are provided to allow users to scale the data for actual operating temperature conditions.



Product Ordering and Shipping Part Number Nomenclature

All SST-10-IRD-810nm products are packaged and labeled with part numbers as outlined in below. When shipped, each reel will contain only a single flux wavelength and V_r bin. The part number designation is as follows:

| SST | — 10 | — IRD | B### | | F###-V# |
|------|-------------|-------|----------|---------------------------------------|---------|
| 33 I | | | D### | · · · · · · · · · · · · · · · · · · · | F###-\ |

| Product Family | Chip Area | Color | Package Configuration | Bin Kit |
|---|-------------|---------------------------------|--|--|
| SST - Ceramic Surface Mount package w/ encapsulation | 10: 1.0 mm² | IRD : Dual Junction Infrared | B90H: 90 deg Beam Angle B130H: 130 deg Beam Angle High Performance Ceramic 3.45mm x 3.45mm See Pages 8-9 for Detailed Drawings | See below for flux, wave- length and forward voltage binning information |

Flux Bins¹

| Bin Code | Radiometric Power at 350mA, t _p =20ms | | | |
|----------|--|-------------------|--|--|
| bin Code | Minimum Flux (mW) | Maximum Flux (mW) | | |
| S | 475 | 505 | | |
| Т | 505 | 535 | | |
| U | 535 | 565 | | |
| V | 565 | 595 | | |
| W | 595 | 625 | | |

Wavelength Bins¹

| Bin Code | Minimum Peak Wavelength (nm) | Maximum Peak Wavelength (nm) |
|----------|------------------------------|------------------------------|
| 810 | 800 | 830 |

Forward Voltage Bins¹

| Bin Code | Minimum Forward Voltage (V) | Maximum Forward Voltage (V) |
|----------|-----------------------------|-----------------------------|
| V9 | 2.8 | 3.0 |
| Va | 3.0 | 3.2 |
| Vb | 3.2 | 3.4 |

| Peak Wavelength | Minimum Flux Bin (mW) | Lens Angle | Ordering Part Number |
|-----------------|--------------------------|------------|-------------------------|
| 910 | 475 | 90 | SST-10-IRD-B90H-S810 |
| 810 | 475 | 130 | SST-10-IRD-B130H-S810 |



Optical and Electrical Characteristics^{1,5}

| Parameter | Complete | Package Type | | Unit |
|---|---|---------------------------------|-------|-------|
| rarameter | Symbol | B90H | B130H | Unit |
| Forward Current | $I_{_f}$ | 350 | | mA |
| Output Power Typical | PO | 53 | 5 | mW |
| Output Power at 1.0A, t = 20ms (typ.) | PO _{1.0A} | 14 | 70 | mW |
| Radiant Intensity at 1.0A, t=20ms (typ.) | ϕ_e | 770 | 410 | mW/sr |
| Minimum Forward Voltage ¹ | $V_{_{fmin}}$ | 2. | 8 | V |
| Forward Voltage Typical | $V_{_f}$ | 3.0 | | V |
| Maximum Forward Voltage ¹ | V _{fmax} | 3.4 | | V |
| Viewing Angle | 2Ø _{1/2} | 90 | 130 | deg |
| Peak Wavelength Typical | $\lambda_{_{P}}$ | 81 | 5 | nm |
| Centroid Wavelength Typical | λ_{c} | 81 | 0 | nm |
| FWHM Typical | Δλ _{1/2} | $\Delta \lambda_{_{1/2}}$ 30 mi | | nm |
| Temperature Coefficient of Foward Voltage TC_{ν_F} -3.0 | | mV/°C | | |
| Temperature Coefficient of Radiometric Power | nperature Coefficient of Radiometric Power TC_{PO} -0.2 | | .2 | %/℃ |
| Temperature Coefficient of Wavelength | TC _λ | 0.3 nm/° | | nm/°C |
| Thermal Resistance (Electrical) | R _{th} | 2. | 4 | °C/W |

Note 1: Binning based on operation at a current of 350mA, 20ms single pulse and a constant junction temperature of $T_j = 25$ °C. Parts are binned and shipped in $0.2VV_t$ increments.




Absolute Maximum Ratings²

| Parameter | Symbol | Rating | Unit |
|--|------------------|----------------------|------|
| Forward Current ^{3,4} | 1 | 1.5 (CW) / 5 (Pulse) | А |
| Power Dissipation | P _D | 6 | W |
| Reverse Voltage | V _R | 5 | V |
| Storage Temperature | T _{stg} | -40 to 100 | °C |
| Junction Temperature ^{3,4} | T, | 115°C | °C |
| ESD Sensitivity (HBM) - JEDEC JS-001-2014 Class 3B | V _{HBM} | ≥8000 | V |
| | V _{CDM} | ≥1000 | V |


- Note 2: To prevent damage refer to operating conditions and derating curves for appropriate maximum operating conditions
- Note 3: Luminus SST-10-IRD-810nm LEDs are designed for operation up to an absolute maximum forward drive current as specified above. Product lifetime data is specified at typical forward drive currents. Sustained operation at absolute maximum currents will result in a reduction of device lifetime compared to typical forward drive currents. Actual device lifetimes will also depend on junction temperature.
- Note 4: Maximum operating case temperature combined with maximum drive current defines the total maximum operating condition for the device. To prevent damage, please operate devices within specified conditions.
- Note 5: Caution must be taken not to stare at the light emitted from these LEDs. Under special circumstances, the high intensity could damage the eye.




Relative Output Flux vs. Forward Current




Relative Output Flux vs. Temperature




Relative Forward Voltage vs. Forward Current




Relative Forward Voltage vs. Temperature



Relative Peak Wavelength vs. Forward Current




Relative Peak Wavelength vs. Temperature







Typical Polar Radiation Plot - B90H




Typical Spectrum



Typical Polar Radiation Plot - B130H




Permissible Pulse Handling Capability






Mechanical Dimensions - B90H Package







Mechanical Dimensions - B130H Package






Tape and Reel - B90H Package






NOTES:


- FINAL TAPE AND REEL PACKAGING MUST MEET THE REQUIREMENTS OF JEDEC-STD-033, LEVEL 2A.
- LEAVE 304.8mm [12.00 in] OF TAPE EMPTY FOR LEAD IN (38 EMPTY POCKETS).
- 3. LEAVE 457.2mm [18.00 in] OF TAPE EMPTY FOR TRAILER (57 EMPTY POCKETS).
- 4. MUST COMPLY TO EIA-481-C-2003








Tape and Reel - B130H Package



SECTION B-B


- LEAVE 457.2mm [18.00 in] OF TAPE EMPTY FOR TRAILER (57 EMPTY POCKETS).
- MUST COMPLY TO EIA-481-C-2003






Reel Packaging

500 parts per reel for B90H Packages - 1,000 parts per reel for B130H Package




Reel Label






Shipping Label



Box Packaging Information






Soldering Profile

| Profile Feature | Sn-Pb Eutectic Assembly | Pb-Free Assembly |
|--|-------------------------|------------------|
| Preheat & Soak | | |
| Temperature min (T _{smin}) | 100°C | 150°C |
| Temperature max (T _{smax}) | 150°C | 200°C |
| Time $(T_{smin} to T_{smax}) (t_s)$ | 60-120 seconds | 60-120 seconds |
| Average ramp-up rate $(T_{smax} \text{ to } T_{p})$ | 3°C/second max | 3°C/second max |
| Liquidus temperature (T ₁) | 183°C | 217°C |
| Time at liquidus (t _L) | 60-150 seconds | 60-150 seconds |
| Peak temperature (T _p) | 235°C | 260°C |
| Time (t _p) within 5°C of the peak tempera- | 20 seconds | 30 seconds |
| ture (Tp) | | |
| Average ramp-down rate $(T_p \text{ to } T_{smax})$ | 6°C/second max | 6°C/second max |
| Time 25°C to peak temperature | 6 minutes max | 8 minutes max |

Note: These are general guidelines. Consult the solder paste manufacturer's datasheet for guidelines specific to the alloy and flux combination used in your application.

Product complies to MSL Level 1 according to JEDEC J-STD-020E





Precautions for Use

Storage:

1. Before opening the package

Unopened LEDs bags should be kept at a temperature between 15°C & 40°C and should be used within a year.

2. After opening the package

Opened LED moisture proof packages should be stored between 30 and 60% RH. The LEDs should be soldered within 168 hours (7days) after opening the package.

If unused LEDs remain on a reel, they should be stored in resealable moisture proof packages with new absorbent material (silica gel) and new moisture indicator cards, or better, in a dry box. If the moisture card indicates, or the first article run of the LEDs popcorns, an oven baking treatment should be performed using the following conditions: 60°C for 20 hours.

The LED electrodes and lead frames may incorporate a silver-plated copper alloy. These can be identified by a silver appearance (compared to a gold appearance). This silver surface may be affected by environmental contaminants, particularly sulfur containing compounds, during storage, and at the point of use. Please avoid conditions which may cause the LEDs to become corroded or discolored. Corrosion or discoloration can reduce solderability and/or affect optical characteristics.

Avoid rapid temperature transitions, especially in high humidity environments where condensation can occur.

Static Electricity:

These products are sensitive to static electricity, and care should be taken when handling them. Static electricity or surge voltage will damage the LEDs. It is recommended to wear an anti-electrostatic wristband or anti-electrostatic gloves when handling the LEDs. All devices, equipment and machinery must be properly grounded. It is recommended that measures be taken to isolate LED processing equipment from potential sources of voltage surges.

Reference: APN-002815 Electrical Stress Damage to LEDs and How to Prevent It

Corrosion Resistance:

Corrosion Test: Class 3B - Test condition: 40°C / 90% RH / 15ppm H2S / 14 days (stricter than IEC60068 2-43)



History of Changes

| Rev | Date | Description of Change |
|-----|------------|-----------------------|
| 01 | 05/19/2021 | Initial Release |

The products, their specifications and other information appearing in this document are subject to change by Luminus Devices without notice. Luminus Devices assumes no liability for errors that may appear in this document, and no liability otherwise arising from the application or use of the product or information contained herein. None of the information provided herein should be considered to be a representation of the fitness or suitability of the product for any particular application or as any other form of warranty. Luminus Devices' product warranties are limited to only such warranties as accompany a purchase contract or purchase order for such products. Nothing herein is to be construed as constituting an additional warranty. No information contained in this publication may be considered as a waiver by Luminus Devices of any intellectual property rights that Luminus Devices may have in such information. Big Chip LEDs™ is a registered trademark of Luminus Devices, Inc., all rights reserved.

This product is protected by U.S. Patents 6,831,302; 7,074,631; 7,083,993; 7,084,434; 7,098,589; 7,105,861; 7,138,666; 7,166,870; 7,166,871; 7,170,100; 7,196,354; 7,211,831; 7,262,550; 7,274,043; 7,301,271; 7,341,880; 7,344,903; 7,345,416; 7,348,603; 7,388,233; 7,391,059 Patents Pending in the U.S. and other countries.