

Electra House, 32 Southtown Road Great Yarmouth, Norfolk NR31 0DU, England Telephone +44 (0)1493 602602 Fax +44 (0)1493 665111 Email:sales@midasdisplays.com www.midasdisplays.com

MDT0144ASS-MULTI		128 x 128 MULTI Interface		MULTI Interface TFT Modu		
MCT0144C6W128128PML			Specification			
Version: 1	1 Date: 18/11/2015					
	Revision					
1	17	7/11/2015	First issue			

Display F	Display Features					
Display Size	1.44"					
Resolution	128 x 128					
Orientation	Portrait					
Appearance	RGB					
Logic Voltage	3.3V		oHS ompliant			
Interface	MULTI	WR				
Brightness	70 cd/m <sup>2</sup>	/ A 20	muliant			
Touchscreen		1 00	mphant			
Module Size	32.86 x 38.00 x 2.60mm					
Operating Temperature	-20°C ~ +70°C					
Pinout	30 way FFC	Box Quantity	Weight / Display			
Pitch	0.5mm	ina - ciu	nnlv			

\* - For full design functionality, please use this specification in conjunction with the ST7735S specification.(Provided Separately)

Display Accessories					
Part Number	Description				
MPBV7	Interconnect board that converts a 30-way FFC to 30 crimp-wire connector.				
MCIB-12	Uno32 Break-out Board with SD Card and LED Backlight Driver. The MCIB-12 Board can be used for any display with a 4 bit, 8 bit, I2C or SPI interface.				

Optional Variants					
Appearances	Voltage				

### **General Description**

#### \* Description

This is a color active matrix TFT (Thin Film Transistor) LCD (liquid crystal display) that uses amorphous sili con TFT as a switching device. This model is composed of a Transmissive type TFT-LCD Panel, driver circuit, back-light unit. The resolution of a 1.44'TFT-LCD contains 128x128 pixels, and can display up to 65K colors.

#### \* Features

-Low Input Voltage: 3.3V(TYP)

-Display Colors of TFT LCD: 65K colors

-RGB Interface: - 8/16-BIT 8080 MCU interface


- 3/4-line SPI

General Information	Specification	Unit	Note
Items	Main Panel	Offic	Note
Display area(AA)	25.50(H)*26.50(V) (1.44inch)	mm	-
Driver element	TFT active matrix	-	-
Display colors	65K	colors	-
Number of pixels	128(RGB)*128	dots	-
Pixel arrangement	RGB vertical stripe	-	-
Pixel pitch	0.1992(H)*0.207(V)	mm	_\/ -
Viewing angle	6:00	o'clock	-
TFT Driver IC	ST7735S	-	-
Display mode	Transmissive/ Normally white	-	-
Operating temperature	-20~ <b>+</b> 70	$^{\circ}$ C	-
Storage temperature	-30∼ <b>+</b> 80	$^{\circ}$ C	-


#### \* Mechanical Information

Item		Min.	Тур.	Max.	Unit	Note
Module size	Horizontal(H)		32.36		mm	-
	Vertical(V)		38.00		mm	-
	Depth(D)		2.60		mm	-
Weight			TBD		g	1

## **Block Diagram**



#### **Outline dimension**



# **Input terminal Pin Assignment**

NO.	SYMBOL		
	3 TIVIDOL	DISCRIPTION	I/O
1	GND	Ground.	Р
2	VCC	Supply voltage (3.3V).	Р
3	IOVCC	Supply voltage for I/O.(1.8V-3V)	Р
4	IMO	IM0='0', MCU 8-bit parallel. IM0='1', MCU 16-bit parallel.	I
5	IM2	MCU parallel interface and serial interface sel ect.  IM2='1', Parallel Interface.  IM2='0', Serial Interface.	1
6	SPI4W	<ul> <li>SPI4W='0', 3-line SPI Enable.</li> <li>SPI4W='1', 4-line SPI Enable.</li> <li>If not used, Fix this pin to DGND.</li> </ul>	
7	DB15		I/O
8	DB14		I/O
9	DB13		1/0
10	DB12		I/O
11	DB11 (	sign • manufacture • i	SUDDI/O
12	DB10		I/O
13	DB09	<ul> <li>DB[15:0] are used as MCU parallel interface data bus</li> </ul>	I/O
14	DB08	- DB0 is the serial input/output signal in serial	I/O
15	DB07	interface mode.	I/O
16	DB06	<ul> <li>In serial interface, DB[15:1] are not used and should be fixed at GND.</li> </ul>	I/O
17	DB05	Siledia de lixea at OND.	I/O
18	DB04		I/O
19	DB03		I/O
20	DB02		I/O
21	DB01		I/O
22	DB0(SPI-SDA)		I/O

23	RD	Read Enable in 8080 MCU Parallel Interface.	1
24	RS(SPI-SCL)	-Display data/command selection pin in MCU InterfaceRS='1': Display data or parameterRS='0': Command dataIn serial interface, this is used as SCLIf not used, please fix this pin at IOVCC or GND level.	I
25	RESET	This signal will reset the device and must be applied to properly initialize the chip.	Ī
26	CS	Chip Selection Pin -Low Enable.	I
27	WR(SPI-RS)	-Write enable in MCU parallel interfaceIn 4-line SPI, this pin is used as RS (data/command selection)If not used, please fix this pin at IOVCC or GND.	I
28	LEDK	Cathode pin of backlight.	Р
29	LEDA	Anode pin of backlight.	Р
30	GND	Ground.	Р

design • manufacture • supply

# **LCD Optical Characteristics**

## **Optical specification**

Item		Symbol	Condition	Min.	Тур.	Max.	Unit.	Note
Transmittance (with Polarizer)		T(%)			5			
Contrast Ratio		CR	Θ=0	500	700			
Response	Rising	T <sub>R</sub>	Normal viewing		5	10		
time	Falling	T <sub>F</sub>			15	25	msec	
Color gan	nut	S(%)		1	40		%	
		W <sub>X</sub>		0.285	0.305	0.325		
	White	$W_Y$		0.314	0.334	0.354		
	Red	R <sub>X</sub>		0.588	0.608	0.628		
Color Filter		R <sub>Y</sub>	1	0.296	0.316	0.336		
Chromacicity		G <sub>X</sub>		0.285	0.305	0.325		
		G <sub>Y</sub>		0.536	0.556	0.576		
		B <sub>X</sub>		0.115	0.135	0.155		
	Blue	B <sub>Y</sub>		0.117	0.137	0.157		
	ues	ΘL	- Manu	ia <u>-</u>	60	3 <u>4</u> P	uty	
\ , n	Hor.	Θr	05.16		60			
Viewing angle		Θυ	CR>10		30			
	Ver.	Θр			60			
Option View D	irection			6 O'clock	<b>(</b>			

## **Measuring Condition**


■ Measuring surrounding: dark room

■ Ambient temperature: 25±2°C

■ 15min. warm-up time.


## **Measuring Equipment**

## Note (1) Definition of Viewing Angle:




Note (2) Definition of Contrast Ratio(CR): measured at the center point of panel


Note (3) Definition of Response Time : Sum of  $T_R$  and  $T_F$ 



Note (4) Definition of optical measurement setup



# Note(5) Rubbing Direction



Viewing From CF Glass Side

### **Electrical Characteristics**

### Absolute Maximum Rating (Ta=25 VSS=0V)

Characteristics	Symbol	Min.	Max.	Unit
Digital Supply Voltage	VDD	-0.3	4.8	V
Digital interface supple Voltage	VDDIO	-0.3	4.6	V
Operating temperature	T <sub>OP</sub>	-20	+70	${\mathbb C}$
Storage temperature	T <sub>ST</sub>	-30	+80	${\mathbb C}$

#### **DC Electrical Characteristics**

Characteristics	Symbol	Min.	Тур.	Max.	Unit	Note
Digital Supply Voltage	VDD	2.4	3.3	4.8	V	
Digital interface supple Voltage	VDDIO	1.65	3.3	4.8	V	
Normal mode Current consumption	IDD		1.2	1	mA	
Loyal input valtage	ViH	0.7VDDIO	ture	VDDIO	V	
Level input voltage	V <sub>IL</sub>	GND		0.3VDDIO	V	
Lovel output voltage	V <sub>OH</sub>	0.8VDDIO		VDDIO	V	
Level output voltage	V <sub>OL</sub>	GND		0.2VDDIO	V	

#### **LED Backlight Characteristics**


The back-light system is edge-lighting type with 2 chips White LED

Item	Symbol	Min.	Тур.	Max.	Unit	Note
Forward Current	I <sub>F</sub>	15	20		mA	
Forward Voltage	V <sub>F</sub>		3.2		V	
LCM Luminance	L <sub>V</sub>	70			cd/m2	lf=20mA

LED life time	Hr	50000	 	Hour	Note1,2
Uniformity	AVg	80	 	%	

Note (1) LED life time (Hr) can be defined as the time in which it continues to operate under the condition: Ta=25±3 °C, typical IL value indicated in the above table until the brightness becomes less than 50%.


Note (2) The "LED life time" is defined as the module brightness decrease to 50% original brightness at Ta=25°C and IL=40mA. The LED lifetime could be decreased if operating IL is larger than 40mA. The constant current driving method is suggested.



design • manufacture • supply

### **AC Characteristic**


# 8080 Series MCU Parallel Interface Timing Characteristics: 16/8-bit Bus



Ta=25 ℃, VDDI=1.65~3.7V, VDD=2.5~4.8V

Signal	Symbol	Parameter	Min	Max	Unit	Description
D/CX	TAST	Address Setup Ttime	0		ns	
DICX	TAHT	Address Hold Time (Write/Read)	10		ns	-
	TCHW	Chip Select "H" Pulse Width	0		ns	
	TCS	Chip Select Setup Time (Write)	15		ns	
csx	TRCS	Chip Select Setup Time (Read ID)	45		ns	
CSA	TRCSFM	Chip Select Setup time (Read FM)	355		ns	-
	TCSF	Chip Select Wait Time (Write/Read)	10		ns	
	TCSH	Chip Select Hold Time	10		ns	
	TWC	Write Cycle	66		ns	
WRX	TWRH	Control Pulse "H" Duration	15		ns	
	TWRL	Control Pulse "L" Duration	15		ns	
	TRC	Read Cycle (ID)	160		ns	
RDX (ID)	TRDH	Control Pulse "H" Duration (ID)	90		ns	When Read ID Data
	TRDL	Control Pulse "L" Duration (ID)	45		ns	


# **Serial Interface Characteristics (3-line Serial)**



Ta=25 °C, VDDI=1.65~3.7V, VDD=2.5~4.8V

Signal	Symbol	Parameter	Min	Max	Unit	Description
	TCSS	Chip Select Setup Time (Write)	15		ns	
	TCSH	Chip Select Hold Time (Write)	15		ns	
CSX	TCSS	Chip Select Setup Time (Read)	60		ns	
	TSCC	Chip Select Hold Time (Read)	65	ure	ns	uppty
	TCHW	Chip Select "H" pulse width	40		ns	
	TSCYCW	Serial Clock Cycle (Write)	66		ns	
	TSHW	SCL "H" Pulse Width (Write)	15		ns	
SCL	TSLW	SCL "L" Pulse Width (Write)	15		ns	
SCL	TSCYCR	Serial Clock Cycle (Read)	150		ns	
	TSHR	SCL "H" Pulse Width (Read)	60		ns	
	TSLR	SCL "L" Pulse Width (Read)	60		ns	
	TSDS	Data Setup Time	10		ns	
SDA	TSDH	Data Hold Time	10		ns	For Maximum CL=30pF
(DIN) (DOUT)	TACC	Access Time	10	50	ns	For Minimum CL=8pF
	ТОН	Output Disable Time	15	50	ns	


# **Serial Interface Characteristics (4-line Serial)**



Ta=25 °C, VDDI=1.65~3.7V, VDD=2.5~4.8V

Signal	Symbol	Parameter	MIN	MAX	Unit	Description
	TCSS	Chip Select Setup Time (Write)	45		ns	
	TCSH	Chip Select Hold Time (Write)	45		ns	
CSX	TCSS	Chip Select Setup Time (Read)	60		ns	
	TSCC	Chip Select Hold Time (Read)	65	re	ns	upply
	TCHW	Chip Select "H" Pulse Width	40		ns	
	TSCYCW	Serial Clock Cycle (Write)	66		ns	-Write Command &
	TSHW	SCL "H" Pulse Width (Write)	15		ns	Data Ram
SCL	TSLW	SCL "L" Pulse Width (Write)	15		ns	Data Nam
SOL	TSCYCR	Serial Clock Cycle (Read)	150		ns	-Read Command &
	TSHR	SCL "H" Pulse Width (Read)	60		ns	Data Ram
	TSLR	SCL "L" Pulse Width (Read)	60		ns	Data Nam
D/CX	TDCS	D/CX Setup Time	10		ns	
DICX	TDCH	D/CX Hold Time	10		ns	
SDA	TSDS	Data Setup Time	10		ns	
(DIN)	TSDH	Data Hold Time	10		ns	For Maximum CL=30pF
(DIN) (DOUT)	TACC	Access Time	10	50	ns	For Minimum CL=8pF
(5001)	TOH	Output Disable Time	15	50	ns	

## **Reset Timing Characteristics**



VDDI=1.65 to 3.3V, VDD=2.4 to 3.3V, AGND=DGND=0V, Ta=-30  $\sim$  70  $^{\circ}$ 


Related Pins	Symbol	Parameter	MIN	MAX	Unit
TRW Reset pulse duration		10	-	us	
RESX	TRT Reset cancel	Poset cancel	- /	5 (Note 1, 5)	ms
		Reset Califer		120 (Note 1, 6, 7)	ms

#### Notes:

- The reset cancel includes also required time for loading ID bytes, VCOM setting and other settings from NVM (or similar device) to registers. This loading is done every time when there is HW reset cancel time (tRT) within 5 ms after a rising edge of RESX.
  - 2. Spike due to an electrostatic discharge on RESX line does not cause irregular system reset according to the table below:

RESX Pulse	Action		
Shorter than 5us	Reset Rejected		
Longer than 9us	Reset		
Between 5us and 9us	Reset starts		

- 3. During the Resetting period, the display will be blanked (The display is entering blanking sequence, which maximum time is 120 ms, when Reset Starts in Sleep Out –mode. The display remains the blank state in Sleep In –mode.) and then return to Default condition for Hardware Reset.
  - 4. Spike Rejection also applies during a valid reset pulse as shown below:



- 5. When Reset applied during Sleep In Mode.
- 6. When Reset applied during Sleep Out Mode.
- It is necessary to wait 5msec after releasing RESX before sending commands. Also Sleep Out command cannot be sent for
   120msec.



#### **LCD Module Out-Going Quality Level**

#### **VISUAL & FUNCTION INSPECTION STANDARD**

#### **Inspection conditions**

Inspection performed under the following conditions is recommended.


Temperature : 25±5°C

Humidity: 65%±10%RH


Viewing Angle: Normal viewing Angle.

Illumination: Single fluorescent lamp (300 to 700Lux)

Viewing distance:30-50cm



#### **Definition**



Zone A: Effective Viewing Area(Character or Digit can be seen)

Zone B: Viewing Area except Zone A

Zone C: Outside (Zone A+Zone B) which can not be seen after assembly by customer.)

Note:

As a general rule ,visual defects in Zone C can be ignored when it doesn't effect product function or appearance after assembly by customer.

## Sampling Plan

According to GB/T 2828-2003 ; , normal inspection, Class  $\,\, II \,\,$  AQL:

Major defect	Minor defect		
0.65	1.5		

LCD: Liquid Crystal Display , TP: Touch Panel , LCM: Liquid Crystal Module

No	Items to be	Criteria	Classification of
	inspected		defects
		1) No display, Open or miss line	
1	Functional defects	2) Display abnormally, Short	
'	Functional defects	3) Backlight no lighting, abnormal lighting.	
		4) TP no function	
2	Missing	Missing component	
3	Outline dimension	Overall outline dimension beyond the drawing	
3	Outline dimension	is not allowed	
4	Color tone	Color unevenness, refer to limited sample	
_	Soldering	Good soldering , Peeling off is not allowed.	Minor
5	appearance		Minor
6	LCD/Polarizer/TP	Black/White spot/line, scratch, crack, etc.	

# Criteria (Visual)

Number	Items	Criteria(mm)				
1.0 LCD Crack/Broken	(1) The edge of LCD broken					
NOTE:		X Y Z				
X: Length Y: Width		≤3.0mm				
Z: Height L: Length of ITO, T: Height of LCD	(2)LCD corner broken	X Y Z ≤3.0mm ≤L ≤T				
	(3) LCD crack	Crack Not allowed				

Number	Items		Crit	eria (mm)	)			
2.0	Spot defect	① light dot (LCD,	/TP/Polarizer bl	ack/white	spot,	light dot,	pinhole, dent,	
	<u> </u>	stain)						
		Zone	Ac	cep able	Qty			
		Size (mm)	Α	В		С		
		Ф≤0.10	Ignoi	re				
		0.10<Φ≤0.20	3( distance	≧10mm)		lanor		
	X	0.20<Φ≤0.25	2			Ignor		
	+ ()( )()(0	Ф > 0.25	0					
$\Phi=(X+Y)/2$	Ф=(X+Y)/2	②Dim spot (LCD/	TP/Polarizer di	m dot, ligl	ht leaka	ige、dark	spot)	
		Zone	Ac	cceptable	Qty			
		Size (mm)	А	В		С		
		Ф≤0.1	Ignor	е				
		0.10<Φ≤0.20	3( distance ≥ 10mm)					
		0.20<Φ≤0.30	2			Ignore		
		Ф>0.30	0					
		③ Polarizer accid	<b>-</b>					
	da	Zone	Acceptable Qty			cunn	\ /	
	u c .	Size (mm)	Α	В		С	Ч	
		Ф≤0.2	Ignore					
		0.3<Φ≤0.5	2( distance ≥ 10mm)			Ignore		
		Ф>0.5	0					
	Line defect							
	(LCD/TP	MC dub (see see)	Law of by Connec	Ac	ceptable	e Qty		
	/Polarizer	Width(mm)	Length(mm	Α	В	С	1	
	black/white line, scratch,	Ф≤0.03	Igno e	Igno	Ignore		1	
	stain)	0.03 <w≤0.05< td=""><td>L≤3.0</td><td>N≤</td><td colspan="2">N≤2</td><td></td></w≤0.05<>	L≤3.0	N≤	N≤2			
	,	0.05 <w≤0.08< td=""><td>L≤2.0</td><td>N≤</td><td>2</td><td></td><td></td></w≤0.08<>	L≤2.0	N≤	2			
		0.08 <w< td=""><td colspan="2">Define as spot defect</td><td>•</td><td></td></w<>	Define as spot defect		•			
							<b>-</b>	

		Zone		Acceptable C			
3.0	Polarizer Bubble	Size (mm)	А	В	С		
3.0	3.0 Dubble	Ф≤0.2	Ignore				
		0.2<Φ≤0.4	3(distance ≥ 10 m)		Ignore		
		0.4<Φ≤0.6	2				
		0.6<Ф					
4.0	SMT	According to IPC-A-610C class II standard . Function defect and missing part are major defect ,the others are minor defect.					

		TP bubble/		A	cceptable Q	tv
			Size Φ(mm)	Α	В	C
		accidented	Ф≤0.1		nore	
		spot	0.1<Φ≤0.25		tance≧	
			0.25<Φ≤0.3		2	Ignore
			0.3<Ф		0	
		Assembly deflection		nd the edge	e of backligh	t ≤0.15mm
5.0	TP Related	Newton Ring	Newton Ring ar NG Newton Ring ar OK			2.排現業性

					似牛顿环
	1				
	TP corner	X	Y	Z	Y
	broken			Z <lcd< td=""><td>X</td></lcd<>	X
	X : length	X≤3.0mm	Y≤3.0mm	thicknes	
	Y: width Z: height	*			
des		Circuitry b	roken is no	ot allowed.	<u>supply</u>
	TP edge	X	Y	Z	x X
	broken X : length			Z <lcd< td=""><td>Z</td></lcd<>	Z
	Y: width	X≤6.0mm	Y≤2.0mm	thicknes	6
	Z : height	* Circuitry broken is not allowed.			

### Criteria (functional items)

Number	Items	Criteria (mm)		
1	No display	Not allowed		
2	Missing segment	Not allowed		
3	Short	Not allowed		
4	Backlight no lighting	Not allowed		
5	TP no function	Not allowed		

Low Temperature Operating Life test	-20℃, 96HR	3ea	pass	-
Thermal Humidity Operating Life test	70℃90%RH, 96HR	3ea	pass	-
Temperature Cycle ON/OFF test	-20°C ↔ 70°C, ON/OFF, 20CYC	3ea	pass	(1)
High Temperature Storage test	80℃, 96HR	3ea	pass	-
Low Temperature Storage test	−30°C, 96HR	3ea	pass	-
ESD test	150pF, 330Ω , ±6KV(Contact)/± 8KV(Air), 5 points/panel, 10 times/point	3ea	pass	
Thermal Shock Resistance	The sample should be allowed to stand the following 5 cycles of operation: TSTL for 30 minutes -> normal temperature for 5 minutes -> TSTH for 30 minutes -> normal temperature for 5 minutes, as one cycle, then taking it out and drying it at normal temperature, and allowing it stand for 24 hours	3ea	pass	
Box Drop Test	1 Corner 3 Edges 6 faces, 66cm(MEDIUM BOX)	1box	pass	-

Note (1) ON Time over 10 seconds, OFF Time under 10 seconds

# **Cautions and Handling Precautions**

#### **Handling and Operating the Module**

- (1) When the module is assembled, it should be attached to the system firmly.
- Do not warp or twist the module during assembly work.
- (2) Protect the module from physical shock or any force. In addition to damage, this may cause improper operation or damage to the module and back-light unit.
- (3) Note that polarizer is very fragile and could be easily damaged. Do not press or scratch the surface.
- (4) Do not allow drops of water or chemicals to remain on the display surface.
- If you have the droplets for a long time, staining and discoloration may occur.
- (5) If the surface of the polarizer is dirty, clean it using some absorbent cotton or soft cloth.
- (6) The desirable cleaners are water, IPA (Isopropyl Alcohol) or Hexane.
- Do not use ketene type materials (ex. Acetone), Ethyl alcohol, Toluene, Ethyl acid or Methyl chloride. It might permanent damage to the polarizer due to chemical reaction.
- (7) If the liquid crystal material leaks from the panel, it should be kept away from the eyes or mouth. In case of contact with hands, legs, or clothes, it must be washed away thoroughly with soap.
- (8) Protect the module from static; it may cause damage to the CMOS ICs.
- (9) Use finger-stalls with soft gloves in order to keep display clean during the incoming inspection and assembly process.
- (10) Do not disassemble the module.
- (11) Protection film for polarizer on the module shall be slowly peeled off just before use so that the electrostatic charge can be minimized.
- (12) Pins of I/F connector shall not be touched directly with bare hands.
- (13) Do not connect, disconnect the module in the "Power ON" condition.
- (14) Power supply should always be turned on/off by the item 6.1 Power On Sequence &6.2 Power Off Sequence

#### **Storage and Transportation.**

- (1) Do not leave the panel in high temperature, and high humidity for a long time.
- It is highly recommended to store the module with temperature from 0 to 35 °C and relative humidity of less than 70%
- (2) Do not store the TFT-LCD module in direct sunlight.
- (3) The module shall be stored in a dark place. When storing the modules for a long time, be sure to adopt effective measures for protecting the modules from strong ultraviolet radiation, sunlight, or fluorescent light.
- (4) It is recommended that the modules should be stored under a condition where no condensation is allowed. Formation of dewdrops may cause an abnormal operation or a failure of the module.
- In particular, the greatest possible care should be taken to prevent any module from being operated where condensation has occurred inside.
- (5) This panel has its circuitry FPC on the bottom side and should be handled carefully in order not to be stressed.