



# **Specification**

Part No.	:	FMA359.A.LBFCG.001
Product Name	:	Steedan 5-in-1 Magnetic Mount Antenna with GNSS, LTE & FirstNet, 2*Wi-Fi
Features :		Low Profile Magnetic Mount Enclosure
		1*LTE 698-960MHz / 1710-2170MHz / 2490-2690MHz /
		3300-3600MHz
		1*FirstNet Band 14
		2* Wi-Fi MIMO 2.4GHz/5.8GHz
		1* GPS-GLONASS-GALILEO-BeiDou Antenna
		IP67 Rated, Ruggedized PC/ABS Enclosure
		LTE & FirstNet: 3M TGC200 Cable and SMA(M)ST Connector
		Wi-Fi: 3M TGC200 Cable and RP SMA(M)ST Connector
		GNSS: 3M RG-174 Cable and SMA(M)ST Connector
		Dimensions: 247 * 144.3 * 47.8 mm
		RoHS Compliant



SPE-18-8-104/A/AW Page 1 of 70





## **1.Introduction**

The Taoglas Steedan Scout FMA359 is a 5-in-1 next-generation low profile magnetic mount antenna for vehicle, outdoor building and heavy equipment roof applications. It has a fully IP67 rated waterproof robust ABS enclosure and base. This is an ideal external combination antenna solution that is used where drilling a hole through the roof of a vehicle or a metal panel is not feasible. It can be mounted on steel surfaces and its ultrastrong neodymium magnets. A soft foam cushion on the base protects the mounting surface during installation and removal. Only 48mm high it mounts discretely to the target application out of sight of most onlookers.

This outstanding antenna delivers powerful antenna technology for LTE (2G/3G/4G) and Wi-Fi 2.4/5.8GHz and a custom tuned GPS/GLONASS/BeiDou patch antenna for GNSS location services. The 5 internal antennas have superior isolation. The LTE antenna also includes backward compatibility to work at most worldwide 3G and 2G bands.

This antenna has been optimized for use in FirstNet Applications. FirstNet is a dedicated communications tool for First Responders in the US. It is an isolated network to provide faster critical information and data-sharing between First Responders and their agencies.

Typical Applications:

- Next Generation OEM Automotive Connectivity
- Multimedia, Navigation and Telematics Systems
- V2V, V2X and Fleet Management Applications
- Real-time HD Video Streaming
- Digital Signage and Remote Monitoring
- FirstNet Responder Routers

FirstNet is a dedicated communications tool for First Responders in the US. It is an isolated network to provide faster critical information and data-sharing between First Responders and their agencies. New FirstNet devices are being deployed to allow for the multitude of services and applications which will be using the network for the following mission critical applications:

- Computer-aided dispatch (vehicle location)
- EMS Electronic Patient Care Reporting
- Vehicle Mounted RMS/ Citations/ Scanners

SPE-18-8-104/A/AW Page 2 of 70





### - Video Streaming

The Steedan is ideal for applications that require highly sophisticated antennas for realtime streaming applications that demand high-speed video uplink and downlink into the cabin of the vehicle. These challenges are resolved by the highly efficient, high gain MIMO antennas, with high isolation, all of which is necessary to achieve the required signal to noise ratio and throughput.

The Steedan can also be customized for your particular wireless application and frequency band, subject to NRE and MOQ. There are 5x 3000mm low loss TGC-200 cables, terminating in SMA(M) connectors for LTE & FirstNet, and RP-SMA(M) for Wi-Fi MIMO. There is a 3000mm RG-174 cable for GNSS terminating in an SMA(M) connector. All cable lengths and connector types are customizable. Contact your regional Taoglas sales office for support.

SPE-18-8-104/A/AW Page 3 of 70





## 2. Specification

### LTE MIMO1 & MIMO 2 on 30x30cm Ground Plane

			LTE	Antenna				
- "			GSM850	GSM900	DCS	PCS	UMTS1	LTE2600
Frequency (MHz)		698~824	824~894	880~960	1710~1880	1850~1990	1920~2170	2490~2690
			Effic	iency (%)	)			
MIMO1	0.3M	42.71	66.20	69.35	54.36	60.18	62.55	65.55
	1M	40.51	63.21	66.22	49.56	54.89	57.63	59.78
	2M	37.81	57.93	60.39	44.17	48.52	50.52	51.94
	3M	34.94	53.80	56.13	39.27	42.70	44.65	45.22
	5M	32.30	49.97	52.18	34.91	37.59	39.46	39.38
	0.3M	43.39	46.55	42.78	49.60	48.61	54.25	64.76
	1M	41.10	44.44	40.85	45.25	44.32	49.96	59.06
MIMO2	2M	38.35	40.72	37.26	40.33	39.16	43.81	51.32
	3M	35.53	37.83	34.62	35.87	34.48	38.70	44.67
	5M	32.91	35.14	32.17	31.90	30.36	34.19	38.90
			Avera	ige Gain (dB	)			
	0.3M	-3.70	-1.79	-1.59	-2.65	-2.21	-2.04	-1.83
	1M	-3.92	-1.99	-1.79	-3.05	-2.61	-2.39	-2.23
MIMO1	2M	-4.22	-2.37	-2.19	-3.55	-3.14	-2.97	-2.85
	3M	-4.57	-2.69	-2.51	-4.06	-3.70	-3.50	-3.45
	5M	-4.91	-3.01	-2.82	-4.57	-4.25	-4.04	-4.05
	0.3M	-3.63	-3.32	-3.69	-3.05	-3.13	-2.66	-1.89
	1M	-3.86	-3.52	-3.89	-3.44	-3.53	-3.01	-2.29
MIMO2	2M	-4.16	-3.90	-4.29	-3.94	-4.07	-3.58	-2.90
	3M	-4.49	-4.22	-4.61	-4.45	-4.62	-4.12	-3.50
	5M	-4.83	-4.54	-4.93	-4.96	-5.18	-4.66	-4.10
Peak Gain (dBi)								
	0.3M	-2.30	-1.57	-1.14	-2.48	-1.83	-1.76	-1.29
	1M	-2.50	-1.77	-1.34	-2.88	-2.23	-2.14	-1.69
MIMO1	2M	-2.80	-2.17	-1.74	-3.38	-2.83	-2.66	-2.30
	3M	-3.20	-2.47	-2.04	-3.88	-3.33	-3.24	-2.94
	5M	-3.60	-2.77	-2.34	-4.38	-3.83	-3.74	-3.54
	0.3M	-2.42	-2.86	-3.13	-2.62	-2.51	-1.80	-1.10
MIMO2	1M	-2.72	-3.06	-3.33	-3.02	-2.91	-2.20	-1.50
	2M	-3.02	-3.46	-3.73	-3.52	-3.51	-2.70	-2.10
	3M	-3.32	-3.76	-4.13	-4.02	-4.01	-3.30	-2.70
	5M	-3.62	-4.06	-4.45	-4.52	-4.51	-3.90	-3.30
Impedance	50 Ω							
Polarization	Linear							

SPE-18-8-104/A/AW Page

Page 4 of 70





SPE-18-8-104/A/AW Page 5 of 70





Wi-F	i Antenna	a (2.4GHz/5.8GHz)		
Frequency (MHz)		2400~2500	4900~5850	
	Effici	iency (%)		
	0.3M	64.14	52.70	
	1M	58.48	45.39	
MIM01	2M	50.93	36.79	
	3M	44.36	29.79	
	5M	38.64	24.13	
	0.3M	44.33	57.67	
	1M	40.43	49.64	
MIMO2	2M	35.21	40.23	
	3M	30.67	32.57	
	5M	26.71	26.37	
	Averag	je Gain (dB)		
	0.3M	-1.93	-2.78	
	1M	-2.33	-3.43	
MIM01	2M	-2.93	-4.34	
	3M	-3.53	-5.26	
	5M	-4.13	-6.17	
	0.3M	-3.53	-2.39	
	1M	-3.93	-3.04	
MIMO2	2M	-4.53	-3.95	
	3M	-5.13	-4.87	
	5M	-5.73	-5.79	
	Peak	Gain (dBi)		
	0.3M	-1.67	-1.95	
	1M	-2.07	-2.55	
MIM01	2M	-2.67	-3.45	
	3M	-3.27	-4.34	
	5M	-3.87	-5.14	
	0.3M	-2.82	-1.65	
	1M	-3.22	-2.35	
MIMO2	2M	-3.82	-3.25	
	3M	-4.42	-4.15	
	5M	-5.02	-5.05	
Impedance		50 Ω		
Return loss	< -6 dB			
Polarization		Linear		

### WI-FI\_MIMO1 and MIMO2\_On 30x30cm Ground Plane

SPE-18-8-104/A/AW Page 6 of 70





GNSS ELECTRICAL				
Frequency	GPS L1: 1575.42 MHz ± 1.023 MHz			
	GLONASS L1: 1602 MHz $\pm$ 1.023 MHz		MHz	
Bandwidth -	6 MHz min			
Return Loss <-10 dB				
Return loss (GPS L1				
GLONASS L1)		< -10 dB		
Passive Gain at Zenith				
(GPS L1 and	+1.0 dBic typ.			
GLONASS L1)				
Polarization	RHCP			
Impedance	50 Ω			
		fo = 1575.42MHz		
LNA Out-band		fo $\pm$ 30 MHz 5dB Min.		
Attenuation	fo ± 50 MHz 20dB Min.			
		fo $\pm$ 100 MHz 25dB Min.		
Input Voltage	Min:1.8V	Typ. 3.0V	Max: 5.5V	
Total Gain @ Zenith	25dBic	30dBic	32dBic	
Current Consumption	6mA	12mA	30mA	
Noise Figure	2.7dB	3.0dB	3.7dB	






MECHANICAL				
Dimensions	247*144.3*47.78 mm			
	LTE & FirstNet: 3000mm TGC200			
Cable	Wi-Fi MIMO & 2: 3000mm TGC200			
	GNSS: 3000mm RG174			
	LTE: SMA(M)			
Connector	Wi-Fi: RP SMA(M)			
	GNSS: SMA(M)			
Casing	PC+ABS			
Adhesive	3M 9448HK + CR4305			
Sealant	Rubber Stopper			
Weight	550 g			
	ENVIRONMENTAL			
Protection	IP67			
Corrosion	5% NaCl for 96hrs - Nickel plated steel base and thread			
Temperature Range	-40°C to +85°C			
Thermal Shock	100 cycles -40°C to +85°C			
Humidity	Non-condensing 65°C 95% RH			
Shock (Drop Test)	1m drop on concrete 6 axes			
Cable Pull	8 Kgf			
Recommended Mounting Torque	24.5N·m			
Maximum Mounting Torque	29.5N⋅m			






## **3.Antenna Characteristics**

### 3.1. LTE MIMO1 and MIMO2 Antennas






SPE-18-8-104/A/AW Page 9 of 70

\*FirstNet® and related logos are trademarks of the U.S. Department of Commerce, First Responder Network Authority. AT&T® is a registered trademark of AT&T Intellectual Property, LLC. Neither the U.S. Department of Commerce nor AT&T have authorized, approved, or endorsed Taoglas or the identified Taoglas products.


SPE-18-8-104/A/AW

Page 10 of 70

### 3.1.3. Average Gain – LTE MIMO1 and MIMO2



### 3.1.4. Peak Gain – LTE MIMO1 and MIMO2









SPE-18-8-104/A/AW Page 11 of 70

\*FirstNet® and related logos are trademarks of the U.S. Department of Commerce, First Responder Network Authority. AT&T® is a registered trademark of AT&T Intellectual Property, LLC. Neither the U.S. Department of Commerce nor AT&T have authorized, approved, or endorsed Taoglas or the identified Taoglas products.





### 3.1.6. ECC – LTE MIMO1 and MIMO2













### 3.2. WI-FI MIMO1 and MIMO2 Antennas




### 3.2.1. Return Loss – WI-FI MIMO1 and MIMO2




SPE-18-8-104/A/AW Page 12 of 70

\*FirstNet® and related logos are trademarks of the U.S. Department of Commerce, First Responder Network Authority. AT&T® is a registered trademark of AT&T Intellectual Property, LLC. Neither the U.S. Department of Commerce nor AT&T have authorized, approved, or endorsed Taoglas or the identified Taoglas products.

### 3.2.3. Average Gain – WI-FI MIMO1 and MIMO2



### 3.2.4. Peak Gain – WI-FI MIMO1 and MIMO2







### SPE-18-8-104/A/AW Page 13 of 70


SPE-18-8-104/A/AW Page 14 of 70


\*FirstNet® and related logos are trademarks of the U.S. Department of Commerce, First Responder Network Authority. AT&T® is a registered trademark of AT&T Intellectual Property, LLC. Neither the U.S. Department of Commerce nor AT&T have authorized, approved, or endorsed Taoglas or the identified Taoglas products.

#### Isolation – WI-FI MIMO1 and MIMO2 3.2.5.

### -5 -10 -15 -20 -25 -30 500 1500 2000 2500 3000 3500 4500 1000 4000 5000 5500

#### ECC – WI-FI MIMO1 and MIMO2 3.2.6.







0









### 3.3. GNSS Antenna

### **3.3.1.** Block Diagram (Active antenna)



### 3.3.2. Return Loss – GNSS Antenna




SPE-18-8-104/A/AW Page 15 of 70






### **3.3.3. Efficiency – GNSS Antenna (passive**



# 3.3.4. Average Gain – GNSS Antenna (passive measurement)



SPE-18-8-104/A/AW Page 16 of 70





# 3.3.5. Peak Gain – GNSS Antenna (passive measurement)




**3.3.6.** Axial Ratio – GNSS Antenna (Zenith is at  $0^{\circ}$ )


Axial Ratio at GPS L1 (1575.42 MHz)

SPE-18-8-104/A/AW Page 17 of 70










### SPE-18-8-104/A/AW Page 18 of 70






### **3.3.7. GNSS Antenna Active Measurements**



## LNA Gain and Noise Figure @ 3.0V







## **4. Antenna Radiation Patterns**

### 4.1 Antenna Setup

On 30\*30cm GND



SPE-18-8-104/A/AW Page 20 of 70





SPE-18-8-104/A/AW Page 21 of 70





2170MHz


2500MHz

Page 22 of 70

### 4.2 2D Radiation Patterns

### 4.2.1 LTE MIMO1\_On 30x30cm GND

### **XY Plane**



\*FirstNet® and related logos are trademarks of the U.S. Department of Commerce, First Responder Network Authority. AT&T® is a registered trademark of AT&T Intellectual Property, LLC. Neither the U.S. Department of Commerce nor AT&T have authorized, approved, or endorsed Taoglas or the identified Taoglas products.

150

(dBi)


SPE-18-8-104/A/AW

210

180








SPE-18-8-104/A/AW Page 23 of 70






### **XZ** Plane



SPE-18-8-104/A/AW Page 24 of 70








SPE-18-8-104/A/AW Page 25 of 70






### **YZ Plane**




SPE-18-8-104/A/AW Page 26 of 70










SPE-18-8-104/A/AW Page 27 of 70





### 4.2.2 LTE MIMO2\_On 30x30cm GND


### **XY Plane**



SPE-18-8-104/A/AW Page 28 of 70








SPE-18-8-104/A/AW Page 29 of 70






### **XZ** Plane



SPE-18-8-104/A/AW Page 30 of 70








SPE-18-8-104/A/AW Page 31 of 70






### **YZ** Plane




SPE-18-8-104/A/AW Page 32 of 70










SPE-18-8-104/A/AW Page 33 of 70





### 4.2.3 WI-FI MIMO1\_On 30x30cm GND

### **XY Plane**




SPE-18-8-104/A/AW Page 34 of 70





### **XZ** Plane




SPE-18-8-104/A/AW Page 35 of 70





### **YZ** Plane




SPE-18-8-104/A/AW Page 36 of 70





## 4.2.4 WI-FI MIMO2\_On 30x30cm GND

#### **XY Plane**




SPE-18-8-104/A/AW Page 37 of 70





### **XZ** Plane





SPE-18-8-104/A/AW Page 38 of 70





### **YZ** Plane





_	●4900MHz	


SPE-18-8-104/A/AW Page 39 of 70






## 4.2.5 GNSS

### **XY Plane**



### **XZ** Plane






1561MHz



**YZ Plane** 









### **3D Radiation Patterns**

### 4.2.6 LTE MIMO1\_ On 30x30cm GND








SPE-18-8-104/A/AW Page 41 of 70














SPE-18-8-104/A/AW Page 42 of 70














SPE-18-8-104/A/AW Page 43 of 70














SPE-18-8-104/A/AW Page 44 of 70












SPE-18-8-104/A/AW Page 45 of 70







SPE-18-8-104/A/AW Page 46 of 70

-10


-20 -25

dB -40






## 4.2.7 LTE MIMO2\_ On 30x30cm GND





SPE-18-8-104/A/AW Page 47 of 70














SPE-18-8-104/A/AW Page 48 of 70














SPE-18-8-104/A/AW Page 49 of 70














SPE-18-8-104/A/AW Page 50 of 70












SPE-18-8-104/A/AW Page 51 of 70









SPE-18-8-104/A/AW Page 52 of 70






### 4.2.8 WI-FI MIMO1\_ On 30x30cm GND










SPE-18-8-104/A/AW Page 53 of 70












SPE-18-8-104/A/AW Page 54 of 70








SPE-18-8-104/A/AW Page 55 of 70





### 4.2.9 WI-FI MIMO2\_ On 30x30cm GND





SPE-18-8-104/A/AW Page 56 of 70


dB -40












SPE-18-8-104/A/AW Page 57 of 70









SPE-18-8-104/A/AW Page 58 of 70






#### 4.1.1 GNSS








SPE-18-8-104/A/AW Page 59 of 70






## 5. Mechanical Drawing (Unit: mm)



	-
	-
/	
	1



	Name	Material	Finish	QT
1	Steeden_Housing_Top	ABS+PC	Black	1
2	Steeden_Housing_Bottom	ABS+PC	Black	1
3	Double Sided Adhesive (Black Foam)	3M CR4305+9448HK	Brown Liner	1
4	Rubber	TPE	Black	1
5	RG174 Coaxial Cable	PVC	Black	1
6	TGC200 Coaxial Cable	PE	Black	4
7	Heat Shrink Tube (GNSS)	PE	Blue Tube/White Text	1
8	Heat Shrink Tube (LTE-1)	PE	Red Tube/White Text	1
9	Heat Shrink Tube (LTE-2)	PE	Red Tube/White Text	1
10	Heat Shrink Tube (Wi-Fi-1)	PE	Yellow Tube/Black Text	1
11	Heat Shrink Tube (Wi-Fi-2)	PE	Yellow Tube/Black Text	1
12	SMA(M)ST for RG174	Brass	Au Plated	1
13	SMA(M)ST for TGC200	Brass	Au Plated	2
14	RP-SMA(M)ST for TGC200	Brass	Au Plated	2

SPE-18-8-104/A/AW


Page 60 of 70





## 6. Packaging

1pc FMA359.A.LBICG.001 per PE Bag PE Bag Dimensions - 300\*150mm Weight - 0.55Kg



12 PE Bags per Carton Box Dimensions - 549\*520\*370mm Weight - 6.6Kg

SPE-18-8-104/A/AW Page 61 of 70






# **7.Application Note**


The FMA359 antenna performance with different cable lengths is shown below.

## 7.1. Return Loss

## Return Loss – LTE MIMO1 Antenna (On 30\*30cm GND)




**Return Loss – LTE MIMO2 Antenna (On 30\*30cm GND)** 

















SPE-18-8-104/A/AW Page 63 of 70






## 7.2. Efficiency



### Efficiency – LTE MIMO1 Antenna (On 30\*30cm GND)

Efficiency – LTE MIMO2 Antenna (On 30\*30cm GND)




SPE-18-8-104/A/AW Page 64 of 70

ke of the U.S. Department of Commerce. First Desponder Network Authority. AT&T@ is a registered trademark of AT&T


SPE-18-8-104/A/AW

Page 65 of 70



















## 7.3. Average Gain




### Average Gain – LTE MIMO2 Antenna (On 30\*30cm GND)




#### SPE-18-8-104/A/AW Page 66 of 70

Average Gain – WI-FI MIMO1 Antenna (On 30\*30cm GND)

TAOGLAS



## Average Gain – WI-FI MIMO2 Antenna (On 30\*30cm GND)




SPE-18-8-104/A/AW Page 67 of 70








## 7.4. Peak Gain



Peak Gain – LTE MIMO2 Antenna (On 30\*30cm GND)




SPE-18-8-104/A/AW Page 68 of 70






Peak Gain – WI-FI MIMO1 Antenna (On 30\*30cm GND)







SPE-18-8-104/A/AW Page 69 of 70





Taoglas makes no warranties based on the accuracy or completeness of the contents of this document and reserves the right to make changes to specifications and product descriptions at any time without notice. Taoglas reserves all rights to this document and the information contained herein.

Reproduction, use or disclosure to third parties without express permission is strictly prohibited.

Copyright © Taoglas Ltd.

SPE-18-8-104/A/AW Page 70 of 70