


Harvatek Surface Mount CHIP LEDs Data Sheet
B3CQ3RBG-02DX001H4U1930



DISCLAIMER.....3

LIFE SUPPORT POLICY.....3

PRODUCT SPECIFICATIONS4

ATTENTION: ELECTROSTATIC DISCHARGE (ESD) PROTECTION4

LABEL SPECIFICATIONS5

SPECIFICATIONS RANGE6

PRODUCT FEATURES8

ELECTRO-OPTICAL CHARACTERISTICS.....8

PACKAGE OUTLINE DIMENSION AND RECOMMENDED SOLDERING PATTERN FOR REFLOW

SOLDERING.....8

ABSOLUTE MAXIMUM RATINGS9

CHARACTERISTICS OF B3CQ3RBG10

PRECAUTION FOR USE11

PACKAGING12

TAPE DIMENSION12

REEL DIMENSION13

PACKING.....13

DRY PACK.....14

BAKING14

PRECAUTIONS.....15

REFLOW SOLDERING15

REWORKING.....16

CLEANING.....16

REVISE HISTORY.....17

Official Product	HT Part No. B3CQ3RBG-02DX001H4U1930	Customer Part No.	Data Sheet No.
Tentative Product	*****	*****	
Specifications are subject to changes for improvement without advance notice. Proprietary data, drawings, company confidential all rights reserved.		07/07/2023	Rev. 1 Page 2/17

DISCLAIMER

HARVATEK reserves the right to make changes without further notice to any products herein to improve reliability, function or design. HARVATEK does not assume any liability arising out of the application or use of any product or circuit described herein; neither does it convey any license under its patent rights, nor the rights of others.

Life Support Policy

HARVATEK's products are not authorized for use as critical components in life support devices or systems without the express written approval of the President of HARVATEK or HARVATEK INTERNATIONAL. As used herein:

1. Life support devices or systems are devices or systems which, (a) are intended for surgical implant into the body, or (b) support or sustain life, and (c) whose failure to perform when properly used in accordance with instructions for use provided in the labeling, can be reasonably expected to result in a significant injury of the user.
2. A critical component in any component of a life support device or system whose failure to perform can be reasonably expected to cause the failure of the life support device or system, or to affect its safety or effectiveness.

Official Product	HT Part No. B3CQ3RBG-02DX001H4U1930	Customer Part No.	Data Sheet No.
Tentative Product	*****	*****	
Specifications are subject to changes for improvement without advance notice. Proprietary data, drawings, company confidential all rights reserved.	07/07/2023	Rev. 1	Page 3/17

Product Specifications

	Specification	Material	Quantity
Luminous Intensity(Iv)	White : 244.5~450 mcd R/G/B@2mA/ Ts= 25°C; Tolerance ±10%		
Chromaticity Coordinate	AS page 7~8 R/G/B@2mA/ Ts= 25°C; Tolerance ± 0.007		
Vf	Red : 2.4 V maximum Green :3.1 V maximum Blue : 3.1V maximum R/G/B@2mA/ Ts= 25°C; Tolerance ± 0.05V		
Ir	<10µA @-5V		
HBM	2KV(R/G/B)		
Resin	Diffused	Epoxy	
Carrier tape	EIA 481-1A specs	Conductive black tape	4000pcs/reel
Reel	EIA 481-1A specs	Conductive black	
Label	HT standard	Paper	
Packing bag	250x230mm	Aluminum laminated bag/Zipper	One reel per bag
Carton	HT standard	Paper	Non-specified

Others:

Each immediate box consists of 5 reels. The 5 reels may not necessarily have the same lot number or the same bin combinations of Iv, λ_D and Vf. Each reel has a label identifying its specification; the immediate box consists of a product label.

Note :This is shipped test conditions

※Remarks: This product should be operated in forward bias. If a reverse voltage is continuously applied to the product, such operation can cause migration resulting in LED damage.

ATTENTION: Electrostatic Discharge (ESD) protection



The symbol to the left denotes that ESD precaution is needed. ESD protection for GaP and AlGaAs based chips is necessary even though they are relatively safe in the presence of low static-electric discharge. Parts built with AlGaInP, GaN, or/and InGaN based chips are **STATIC SENSITIVE devices**. ESD precaution must be taken during design and assembly.

If manual work or processing is needed, please ensure the device is adequately protected from ESD during the process.

Official Product	HT Part No. B3CQ3RBG-02DX001H4U1930	Customer Part No.	Data Sheet No.
Tentative Product	*****	*****	
Specifications are subject to changes for improvement without advance notice. Proprietary data, drawings, company confidential all rights reserved.		07/07/2023	Rev. 1 Page 4/17

Label Specifications



■ Harvatek P/N:

B 3CQ 3 RBG- 02D- X001 H4

Product	Package size	Dice Q'ty	Color	Current	Series Number	Taping
B:PCB	0.95(L) x 0.95(W) x 0.25(H) mm	3:TRI	RBG(Full color)	R/G/B:2mA D:Diffused	X001~XZZZ	1. Taping style 2. Q'ty

■ Lot No.

1	2	3	4	5	6	7	8	9	10
E	1	A	1	A	2	2	L	1	2
Code 1 2		Code 3	Code 4	Code 5	Code 6	Code 7	Code 8	Code 9	Code 10
		Mfg. Year	Mfg. Month	Mfg. Date	Consecutive number		Special code		
Internal Tracing Code		2020-L		1:A	01~ZZ		000~ZZZ		
		2021-M		2:B					
		2022-P	1:Jan.	3:C					
		2023-Q	2:Feb.	...					
		26:Z					
		2026-T	A:Oct.	27:7					
		2027-V	B:Nov.	28:8					
...	C:Dec.	29:9							
2030-Y		30:3							
2031-Z		31:4							
...									

Official Product	HT Part No. B3CQ3RBG-02DX001H4U1930	Customer Part No.	Data Sheet No.
Tentative Product	*****	*****	
Specifications are subject to changes for improvement without advance notice. Proprietary data, drawings, company confidential all rights reserved.		07/07/2023	Rev. 1
			Page 5/17

Specifications Range

Luminous Intensity (Iv) Bin:R/G/B @2mA

Color	Bin Code	MIN	MAX	Condition
White	Sc	244.5	285	R: IF=2mA
	T	285	360	G: IF=2mA
	U	360	450	B: IF=2mA

Note: It maintains a tolerance of $\pm 10\%$ on Luminous Intensity


Color Bin:

Color	Bin Code	CIE_x / CIE_y		Bin Code	CIE_x / CIE_y		Bin Code	CIE_x / CIE_y		Bin Code	CIE_x / CIE_y	
White	W9	0.24	0.24	W10	0.24	0.26	W11	0.24	0.28	W12	0.22	0.30
		0.24	0.26		0.24	0.28		0.24	0.30		0.24	0.30
		0.22	0.26		0.22	0.28		0.22	0.30		0.24	0.32
		0.22	0.24		0.22	0.26		0.22	0.28		0.22	0.32
	W13	0.26	0.24	W14	0.26	0.26	W15	0.26	0.28	W16	0.24	0.30
		0.26	0.26		0.26	0.28		0.26	0.30		0.26	0.30
		0.24	0.26		0.24	0.28		0.24	0.30		0.26	0.32
		0.24	0.24		0.24	0.26		0.24	0.28		0.24	0.32
	W17	0.28	0.24	W18	0.28	0.26	W19	0.28	0.28	W20	0.26	0.30
		0.28	0.26		0.28	0.28		0.28	0.30		0.28	0.30
		0.26	0.26		0.26	0.28		0.26	0.30		0.28	0.32
		0.26	0.24		0.26	0.26		0.26	0.28		0.26	0.32

Note: It maintains a tolerance of $x,y \pm 0.007$

Official Product	HT Part No. B3CQ3RBG-02DX001H4U1930	Customer Part No.	Data Sheet No.
Tentative Product	*****	*****	
Specifications are subject to changes for improvement without advance notice. Proprietary data, drawings, company confidential all rights reserved.		07/07/2023	Rev. 1
			Page 6/17

CIE Chromaticity Diagram



Forward Voltage (Vf) Bin:

HT-B3CQ3RBG Series								
Vf								
Red			Green			Blue		
E18	1.6	2.4	F2A	2.1	3.1	F2A	2.1	3.1

Note: It maintains a tolerance of $\pm 0.05V$ on forward voltage measurements

Official Product	HT Part No. B3CQ3RBG-02DX001H4U1930	Customer Part No.	Data Sheet No.
Tentative Product	*****	*****	
Specifications are subject to changes for improvement without advance notice. Proprietary data, drawings, company confidential all rights reserved.		07/07/2023	Rev. 1
			Page 7/17

Product Features

Electro-Optical Characteristics

(T_{Soldering}, 25°C)

Part number	Emitting Color	Forward Voltage(VF)		Wavelength (nm)	IV(mcd)	Viewing Angle 2θ1/2
		typ.	max.			
B3CQ3RBG	Red	2.0	2.4	White	244.5~450	>120 deg.
	Green	2.5	3.1			
	Blue	2.7	3.1			

Package Outline Dimension and Recommended Soldering Pattern for Reflow Soldering

Unit: mm Tolerance: +/-0.1

Outline Dim.	Soldering Pattern

Soldering terminals may shift in the x, y direction.

Official Product	HT Part No. B3CQ3RBG-02DX001H4U1930	Customer Part No.	Data Sheet No.
Tentative Product	*****	*****	
Specifications are subject to changes for improvement without advance notice. Proprietary data, drawings, company confidential all rights reserved.	07/07/2023	Rev. 1	Page 8/17

Absolute Maximum Ratings

(T_S 25°C)

Series	P _D (mW)	I _F (mA)	IFP (mA)	T _{OP} (°C)	T _{ST} (°C)
Color	Power Dissipation	Forward Current	Pulse Forward Current	Operation Temperature	Storage Temperature
Red	4.8	2	60	-30~+80	-40~+85
Blue/Green	6.2	2			


*Condition for I_{FP} is pulse of 1/10 duty and 0.1msec width

*Remarks: This product should be operated in forward bias. If a reverse voltage is continuously applied to the product, such operation can cause migration resulting in LED damage.


Official Product	HT Part No. B3CQ3RBG-02DX001H4U1930	Customer Part No.		Data Sheet No.
Tentative Product	*****	*****		
Specifications are subject to changes for improvement without advance notice. Proprietary data, drawings, company confidential all rights reserved.		07/07/2023	Rev. 1	Page 9/17

Characteristics of B3CQ3RBG


Relative Intensity vs. Forward Current




Forward Voltage vs. Forward Current




Relative Intensity vs. Wavelength



Wavelength vs. Forward Current



Radiation Diagram



Official Product	HT Part No. B3CQ3RBG-02DX001H4U1930	Customer Part No.	Data Sheet No.
Tentative Product	*****	*****	
Specifications are subject to changes for improvement without advance notice. Proprietary data, drawings, company confidential all rights reserved.	07/07/2023	Rev. 1	Page 10/17


Precaution for Use

1. The chips should not be used directly in any type of fluid such as water, oil, organic solvent, etc.
2. When the LEDs are illuminating, the maximum ambient temperature should be first considered before operation.
3. LEDs must be stored in a clean environment. A sealed container with a nitrogen atmosphere is necessary if the storage period is over 3 months after shipping.
4. The LEDs must be used within seven days after unpacked. Unused products must be repacked in an anti-electrostatic package, folded to close any opening and then stored in a dry and cool space.
5. The appearance and specifications of the products may be modified for improvement without further notice.
6. The LEDs are sensitive to the static electricity and surge. It is strongly recommended to use a grounded wrist band and anti-electrostatic glove when handling the LEDs. If a voltage over the absolute maximum rating is applied to LEDs, it will damage LEDs. Damaged LEDs will show some abnormal characteristics such as remarkable increase of leak current, lower turn-on voltage and getting unlit at low current.

Official Product	HT Part No. B3CQ3RBG-02DX001H4U1930	Customer Part No.	Data Sheet No.
Tentative Product	*****	*****	
Specifications are subject to changes for improvement without advance notice. Proprietary data, drawings, company confidential all rights reserved.	07/07/2023	Rev. 1	Page 11/17


Packaging

Tape Dimension




Dim. A	Dim. B	Dim. C	Q'ty/Reel
1.11±0.05	1.11±0.05	0.35±0.05	4K

Unit: mm




Official Product	HT Part No. B3CQ3RBG-02DX001H4U1930	Customer Part No.	Data Sheet No.
Tentative Product	*****	*****	
Specifications are subject to changes for improvement without advance notice. Proprietary data, drawings, company confidential all rights reserved.		07/07/2023	Rev. 1
			Page 12/17

Reel Dimension



Packing



5 or 10 boxes per carton is available depending on shipment quantity.


Official Product	HT Part No. B3CQ3RBG-02DX001H4U1930	Customer Part No.	Data Sheet No.
Tentative Product	*****	*****	
Specifications are subject to changes for improvement without advance notice. Proprietary data, drawings, company confidential all rights reserved.		07/07/2023	Rev. 1
			Page 13/17

Dry Pack

All SMD optical devices are **MOISTURE SENSITIVE**. Avoid exposure to moisture at all times during transportation or storage. Every reel is packaged in a moisture protected anti-static bag. Each bag is properly sealed prior to shipment.

Upon request, a humidity indicator will be included in the moisture protected anti-static bag prior to shipment.

The packaging sequence is as follows:



Baking

Baking before soldering is recommended when the package has been unsealed for 4 weeks.

The conditions are as followings:

60±3°C × (12~24hrs) and <5%RH, taped reel type.

100±3°C × (45min~1hr), bulk type.

130±3°C × (15min~30min), bulk type.

Official Product	HT Part No. B3CQ3RBG-02DX001H4U1930	Customer Part No.	Data Sheet No.
Tentative Product	*****	*****	
Specifications are subject to changes for improvement without advance notice. Proprietary data, drawings, company confidential all rights reserved.		07/07/2023	Rev. 1
			Page 14/17


PRECAUTIONS

1. Avoid exposure to moisture at all times during transportation or storage.
2. Anti-Static precaution must be taken when handling GaN, InGaN, and AlGaInP products.
3. It is suggested to connect the unit with a current limiting resistor of the proper size. Avoid applying a reverse voltage beyond the specified limit.
4. Avoid operation beyond the limits as specified by the absolute maximum ratings.
5. Avoid direct contact with the surface through which the LED emits light.
6. If possible, assemble the unit in a clean room or dust-free environment.

Reflow Soldering

Recommend soldering paste specifications:

1. Operating temp.: Above 217°C, 60 ~ 150 sec.
2. Peak temp.: 260°C Max. 10 sec Max.
3. Reflow soldering should not be done more than two times.
4. Never attempt next process until the component is cooled down to room temperature after reflow.
5. The recommended reflow soldering profile (measured on the surface of the LED terminal) is as following: Lead free solder profile



Temperature vs. Time

Official Product	HT Part No. B3CQ3RBG-02DX001H4U1930	Customer Part No.	Data Sheet No.
Tentative Product	*****	*****	
Specifications are subject to changes for improvement without advance notice. Proprietary data, drawings, company confidential all rights reserved.		07/07/2023	Rev. 1
			Page 15/17

Reworking

- Rework should be completed within 5 seconds under 260°C.
- The iron tip must not come in contact with the copper foil.
- Twin-head type is preferred.

Cleaning

Following are cleaning procedures after soldering:

- An alcohol-based solvent such as isopropyl alcohol (IPA) is recommended.
- Temperature x Time should be 50°C x 30sec. or <30°C x 3min
- Ultra sonic cleaning: < 15W/ bath; bath volume ≤ 1liter
- Curing: 100°C max, <3min

Cautions of Pick and Place

- Avoid stress on the resin at elevated temperature.
- Avoid rubbing or scraping the resin by any object.
- Electric-static may cause damage to the component. Please ensure that the equipment is properly grounded. Use of an ionizer fan is recommended.

Official Product	HT Part No. B3CQ3RBG-02DX001H4U1930	Customer Part No.	Data Sheet No.
Tentative Product	*****	*****	
Specifications are subject to changes for improvement without advance notice. Proprietary data, drawings, company confidential all rights reserved.	07/07/2023	Rev. 1	Page 16/17

Revise History

Rev.	Descriptions	Date	Page
1		07/07/2023	

Official Product	HT Part No. B3CQ3RBG-02DX001H4U1930	Customer Part No.	Data Sheet No.
Tentative Product	*****	*****	
Specifications are subject to changes for improvement without advance notice. Proprietary data, drawings, company confidential all rights reserved.		07/07/2023	Rev. 1
			Page 17/17