

SPECIFICATIONS					
CUSTOMER	- CNO003				
SAMPLE CODE	SMA800480T030-ZHC				
MASS PRODUCTION CODE	HMA800480T030-ZHC				
SAMPLE VERSION	. 01				
SPECIFICATIONS EDITION	. 002				
DRAWING NO. (Ver.)	: LMD-HMA800480T030-ZHC(Ver.002)				
PACKAGING NO. (Ver.)	: PKG- HMA800480T030-ZHC(Ver.001)				

Customer Approved

Date:

	A	pproved	Chec	ked	Designer			
	C	林裘中 Daniel Lin	溪 s Lu	陳漢霖 Hans Chen				
		iminary specification cification for sample	2022.01.13 TW RD APR					
		P	OWERTIP T	ECH. CORP.				
Head	lquarters:	S: No.8, 6 th Road, Taichung Industrial Park, Taichung, Taiwan TEL: 886-4-2355-8168 E-mail: <u>sales@powertip.com.tw</u>						
		台中市 407 工業區六路 85	虎	FAX: 886-4-2355-8166	Http://www.powertip.com.tw			



History of Version

Date (mm / dd / yyyy)	Ver.	Edi.	Description	Page	Design by
03/03/2021	01	001	Preliminary	-	Hans
12/01/2021	01	002	1. First Sample 2. Add J13 Connector 3. Modify Board Size & Add J13	- 13 Appendix	Hans
					/



CONTENTS

1. SPECIFICATIONS

- 1.1 Features
- 1.2 Mechanical Specifications
- **1.3 Absolute Maximum Ratings**
- **1.4 DC Electrical Characteristics**
- **1.5 Optical Characteristics**

2. MODULE STRUCTURE

- 2.1 Counter Drawing
- 2.2 Interface Pin Description

3. QUALITY ASSURANCE SYSTEM

3.1 Quality Assurance Flow Chart

4. RELIABILITY TEST

4.1 Reliability Test Condition

5. PRECAUTION RELATING PRODUCT HANDLING

- 5.1 Safety
- 5.2 Handling
- 5.3 Storage
- 5.4 Terms of Warranty

APPENDIX

- 1. Drawing
- 2.PKG Drawing



1. SPECIFICATIONS

1.1 Features

Hardware

RISC Processor	STM32H750 480 MHz, ARM Cortex-M7
RAM	16MB SDRAM
Flash	32MB QSPI FLASH 8GB eMMC
External Storage	1 x Micro SD (max. 32G)
Resolution	800 * 3 (RGB) * 480 Dots
Viewing Direction	Full Viewing Angle
Interface	Parallel RGB 24 bits
USB	1 x USB2.0 Device
Serial	1 x UART, 1 x SPI, 1 x I2C, 1 x CAN
RMII	1 x Ethernet
DC	5V
	RAM Flash External Storage Resolution Viewing Direction Interface USB Serial RMII

Note:

- 1. Support Micro USB Power Supply.
- 2. Support USB Device Full Speed.
- 3. Support CAN Bus (Compatible with ISO11898-2).
- 4. Support Ethernet (10BASE-T / 100BASE-T).
- 5. Support RTC.



1.2 Mechanical Specifications

ltem	Standard Value	Unit
Outline Dimension	131.0(W) x 90.5(L) x 14.0(H) MAX	mm
Active Area	108.0 (W) x 64.8(L)	mm

1.3 Absolute Maximum Ratings

Ta = 25°C

Item	Symbol	Condition	Min.	Max.	Unit
Power Supply	VIN		4.5	6.0	V
Operating Temperature	Тор		-20	70	S
Storage Temperature	Тsт		-30	80	°C
Humidity	HD	Ta=60 °C	10	90	%RH

1.4 DC Electrical Characteristics

Ta = 25℃

Item	Sym bol	Condition	Min.	Тур.	Max.	Unit
	DOI					
Power Supply Voltage	VIN	-	4.5	5	5.5	V
Power Supply Voltage of RTC	VBAT	-	2.0		3.6	V
Power Supply Current	IIN	VIN = 5V	-	600	-	mA
Power Consumption of System	PIN	VIN = 5V	-	3	-	W
High-Level voltage of digital input	VIH	-	2.3	-	-	V
Low-Level voltage of digital input	VIL	-	-	-	0.9	V
High level voltage of digital output	Vон	-	2.4	-	-	V
Low level voltage of digital output	Vol	-	-	-	0.4	V



1.5 Optical Characteristics

VDD= 3.3 V, Ta=25 ℃

Item	Symbol		Condition	Min.	Тур.	Max.	unit	-
Response time		Tr+Tf	Ta = 25 ℃ θX, θY = 0°	-	37	56	ms	Note 2
	Тор	θY+		4	80	-		
	Bottom	θY-	CR ≥ 10		80	-	Deg	Note 4
Viewing angle	Left	θX-			80	-	Deg.	Note 4
	Right	θX+			80	-		
Contrast ratio		CR		650	800	-	-	Note 3
	White	Х		0.27	0.32	0.37		
	vvnite	Y	T- 05 %	0.30	0.35	0.40	-	Note1
	Ded	Х		0.56	0.61	0.66		
Color of CIE	Red	Y	Ta = 25 ℃	0.30	0.35	0.40		
Coordinate (With B/L & T/P)	Orean	Х	$\Theta X, \Theta Y = 0^{\circ}$	0.31	0.36	0.41	_	Note1
$(\mathbf{V} \mathbf{U} \mathbf{U} \mathbf{D} \mathbf{L} \mathbf{\alpha} \mathbf{I} \mathbf{F})$	Green	Y		0.53	0.58	0.63	1	
	Dhua	Х		0.08	0.13	0.18		
	Blue	Y		0.06	0.11	0.16		
Average Brightness Pattern=white			PWM="High"					
display (With B/L & T/P) *1		IV	(Duty=100%)	680	850	-	cd/m2	Note1
Uniformity (With B/L & T/P)*2		ΔB	PWM="High" (Duty=100%)	70	-	-	%	Note1




Note 1:

- *1: △B=B(min) / B(max) * 100%
- *2: Measurement Condition for Optical Characteristics:

a: Environment: $25^{\circ}C \pm 5^{\circ}C / 60\pm 20\%$ R.H, no wind, dark room below 10 Lux at typical lamp current and typical operating frequency

- b: Measurement Distance: 500 \pm 50 mm, (θ = 0 °)
- c: Equipment: TOPCON BM-7 fast, (field 1°), after 10 minutes operation
- d: The uncertainty of the C.I.E coordinate measurement ±0.01, Average Brightness ± 4%






To be measured at the center area of panel with a viewing cone of 1° by Topcon luminance meter BM-7, after 10 minutes operation (module)

Note 2: Definition of response time:


The output signals of photo detector are measured when the input signals are changed from "black" to "white" (falling time) and from "white" to "black" (rising time), respectively. The response time is defined as the time interval between the 10% and 90% of Amplitudes. Refer to figure as below:

Normally White





Normally Black






2. MODULE STRUCTURE

2.1 Counter Drawing



- * See Appendix
- 2.1.2 Block Diagram



POWERTIP

2.2 Interface Pin Description

JT1 --- JTAG (Wafer Pitch1.25mm 6pin)

Pin No.	Symbol	Туре	DESCRIPTION
1	PA15	Ю	General Purpose I/O, Port A [15].
2	PA8	Ю	General Purpose I/O, Port A [8].
3	RESETINn	I	JTAG test reset.
4	JTMS/SWDIO	I/O	JTAG test mode select / Serial wire data in/out.
5	JTCK/SWCLK	I	JTAG test clock / Serial wire clock.
6	GND	Р	Ground.

J3 --- CAN Bus (Wafer Pitch1.25mm 2pin)


Pin No.	Symbol	Туре	DESCRIPTION
1	CAN H	DS	High Level CAN Bus Line.
2	CAN L	DS	Low Level CAN Bus Line.

J4 ---- USB 2.0 Device MICRO USB

Pin No.	Symbol	Туре	DESCRIPTION
1	VBUS5V	Р	+5.0V
2	D-	DS	Data – (Data M)
3	D+	DS	Data + (Data P)
4	ID	-	Not Used.



Pin No.	Symbol	Туре	DESCRIPTION
5	GND	Ρ	Ground
5	GND		Glound



J8 --- RTC (Wafer Pitch1.25mm 2pin)

Pin No.	Symbol	Туре	DESCRIPTION	
1	VBAT	Ρ	Power Supply for RTC.	
2	GND	Р	Ground.	

J6 --- Ethernet (Wafer Pitch1.25mm 10pin)

Pin No.	Symbol	Туре	DESCRIPTION			
1	GND	Р	Ground.			
2	GND	Р	Ground.			
3	LED_ACK	0	Link Speed LED Indication. (See Note 1)			
4	RXD-	DS	Receive Negative.			
5	RXD+	DS	Receive Positive.			
6	TXD-	DS	Transmit Negative.			
7	TXD+	DS	Transmit Positive.			
8	LED_LINK	0	Link Activity LED Indication. (See Note 2)			
9	GND	Р	Ground.			
10	VDD3V3	Р	Power Supply (+3.3V).			

Note 1: This pin is driven active when the operating speed is 100Mbps. It is inactive when the operating speed is 10Mbps or during line isolation.

Note 2: This pin is driven active when a valid link is detected and blinks when activity is detected.

POWERTIP

J10 --- P05D00071-01 Interface Reserved (Pitch 0.5mm 30pin Double contact)

Pin No.	Symbol	Туре	DESCRIPTION	
1	GND	Р	Ground.	
2	PG3	IO	General Purpose I/O, Port G [3].	
3	PB2	IO	General Purpose I/O, Port B [2].	
4	NC	-	Not Used.	
5	GND	Р	Ground.	
6	I2C_CLK	IO	I2C2 CLK, Function Reserved.	
7	GND	Р	Ground.	
8	I2C_DAT	IO	I2C2 DAT, Function Reserved.	
9	GND	Р	Ground.	
10	SPI_CLK	IO	SPI1 CLK, Function Reserved.	
11	GND	Р	Ground.	
12	SPI_MISO	IO	SPI1 MISO, Function Reserved.	
13	SPI_MOSI	IO	SPI1 MOSI, Function Reserved.	
14	GND	Р	Ground.	
15	SPI_CS0	IO	SPI1 CS0, Function Reserved.	
16	GND	Р	Ground.	
17	PH6	IO	General Purpose I/O, Port H [6].	
18	PH7	Ю	General Purpose I/O, Port H [7].	
19	PH5	10	General Purpose I/O, Port H [5].	
20	PB1	IO	General Purpose I/O, Port B [1].	
21	GND	Р	Ground.	
22	RESETINn		System Reset, Active Low.	
23	UART_TXD	IO	USART2 TX, Function Reserved.	
24	UART_RXD	IO	USART2 RX, Function Reserved.	
25	GND	Р	Ground.	
26	VIN	Р	Power Supply (+5.0V).	
27	VIN	Р	Power Supply (+5.0V).	
28	UART_RTS	10	USART2 RTS, Function Reserved.	
29	UART_CTS	10	USART2 CTS, Function Reserved.	
30	GND	Р	Ground.	




J13 --- Power Input (Wafer Pitch1.25mm 4pin)

Pin No.	Symbol	Туре	DESCRIPTION
1	VBUS5V	Р	+5.0V
2	VBUS5V	Р	+5.0V
3	GND	Р	Ground
4	GND	Р	Ground



3. QUALITY ASSURANCE SYSTEM

3.1 Quality Assurance Flow Chart





Item	Customer	Sales	R&D	Q.A	Manufact uring	Product control	Purchase	Inventory control
Sales Service	Info	Claim	[Trackin	Failure an Corrective			
Q.A Activity	 ISO 9001 Maintenance Activities Equipment calibration Standardization Management Process improvement proposal Education And Training Activities 							



4. RELIABILITY TEST

4.1 Reliability Test Condition

NO.	TEST ITEM TEST CONDITION					
1	High Temperature Storage Test	Keep in +80 ±2℃ 96 hrs Surrounding temperature, then storage at normal condition 4hrs.				
2	Low Temperature Storage Test	·				
3	High Temperature / High Humidity Storage Test	Keep in +60°C / 90% R.H duration for 96 hrs Surrounding temperature, then storage at normal condition 4hrs. (Excluding the polarizer)				
4	Temperature Cycling Storage Test	$30^{\circ}C \rightarrow +25^{\circ}C \rightarrow +80^{\circ}C \rightarrow +25^{\circ}C$ $(30^{\circ}mins) (5^{\circ}mins) (30^{\circ}mins) (5^{\circ}mins)$ $10^{\circ}Cycle$ Surrounding temperature, then storage at normal condition 4hrs.				
5	Vibration Test (Packaged)	 Sine wave 10~55 Hz frequency (1 min) The amplitude of vibration :1.5 mm Each direction (X \ Y \ Z) duration for 2 Hrs 				
6	Drop Test (Packaged)	Packing Weight (Kg) Drop Height (cm) 0 ~ 45.4 122 45.4 ~ 90.8 76 90.8 ~ 454 61 Over 454 46				



5. PRECAUTION RELATING PRODUCT HANDLING

5.1 SAFETY

- 5.1.1 If the LCD panel breaks, be careful not to get the liquid crystal to touch your skin.
- 5.1.2 If the liquid crystal touches your skin or clothes, please wash it off immediately by using soap and water.

5.2 HANDLING

- 5.2.1 Avoid any strong mechanical shock which can break the glass.
- 5.2.2 Avoid static electricity which can damage the CMOS LSI—When working with the module, be sure to ground your body and any electrical equipment you may be using.
- 5.2.3 Do not remove the panel or frame from the module.
- 5.2.4 The polarizing plate of the display is very fragile. So, please handle it very carefully, do not touch, push or rub the exposed polarizing with anything harder than an HB pencil lead (glass, tweezers, etc.)
- 5.2.5 Do not wipe the polarizing plate with a dry cloth, as it may easily scratch the surface of plate.
- 5.2.6 Do not touch the display area with bare hands, this will stain the display area.
- 5.2.7 Do not use ketonic solvent & aromatic solvent. Use with a soft cloth soaked with a cleaning naphtha solvent.
- 5.2.8 To control temperature and time of soldering is $320 \pm 10^{\circ}$ C and $3 \sim 5$ sec.
- 5.2.9 To avoid liquid (include organic solvent) stained on LCM.
- 5.2.10 Caution! (LCM products with Capacitive Touch Panel) Strong EMI-sources such as switch-mode power supplies (SPS) can lead to touch malfunction (e.g., ghost-touches). Therefore, the touch needs to be thoroughly tested inside the target application.
- 5.2.11 CAUTION: Continuously displaying same static image will result in high possibility of image sticking/image burn-in effect due to TFT panel characteristic.
- 5.2.12 Double-sided tape designed to be attached with the customer's mechanical device, please follow up the rules and regulations published by the original manufacturer of double-side tape for the attachment operation.

5.3 STORAGE

- 5.3.1 Store the panel or module in a dark place where the temperature is $25^{\circ}C \pm 5^{\circ}C$ and the humidity is below 65% RH.
- 5.3.2 Do not place the module near organics solvents or corrosive gases.
- 5.3.3 Do not crush, shake, or jolt the module.

5.4 TERMS OF WARRANTY

- 5.4.1 Applicable warrant period The period is within thirteen months since the date of shipping out under normal using and storage conditions.
- 5.4.2 Unaccepted responsibility

This product has been manufactured to your company's specification as a part for use in your company's general electronic products. It is guaranteed to perform according to delivery specifications. For any other use apart from general electronic equipment, we cannot take responsibility if the product is used in nuclear power control equipment, aerospace equipment, fire and security systems or any other applications in which there is a direct risk to human life and where extremely high levels of reliability are required.

