



Selector Guide

Summer/Fall 2017



ALPHA & OMEGA
SEMICONDUCTOR

Powering a Greener Future™

DIVERSE CUSTOMER BASE

Telecom	Consumer		PC	Industrial
	Black Goods	White Goods		
<ul style="list-style-type: none"> ▪ Alcatel-Lucent ▪ Belfuse ▪ Delta ▪ Efore ▪ Emerson ▪ H3C ▪ Murata ▪ Nokia Siemens Networks ▪ ZTE 	<ul style="list-style-type: none"> ▪ Changhong ▪ Haier ▪ Hisense ▪ LG ▪ Samsung ▪ Sony ▪ TCL 	<ul style="list-style-type: none"> ▪ Changhong ▪ Cuckoo ▪ Haier ▪ Hisense ▪ Microsteps ▪ Midea ▪ Nidec ▪ Panasonic ▪ Sanyo 	<ul style="list-style-type: none"> ▪ Acer ▪ Asus ▪ Dell ▪ Hewlett Packard ▪ Lenovo 	<ul style="list-style-type: none"> ▪ BYD ▪ Chicony ▪ Delta ▪ Emerson ▪ Philips ▪ Tyco

CERTIFICATIONS FOR AOS & APM PLANTS:

- ISO 9001 (Quality Management System)
- ISO 14001 (Environmental Management System)
- QC 080000 (Hazardous Substance Management System)
- Sony's Green Partner Program
- ISO 14064 (Greenhouse Gasses)
- TS 16949 (Automotive)

PASSED AUDITS BY MAJOR CUSTOMERS:

- Alcatel-Lucent
- Dell
- Delta
- Emerson
- General Electric
- Hewlett Packard
- Huawei
- Lenovo
- LG
- Microsoft
- Motorola
- Nokia Siemens Networks
- Panasonic
- Philips
- Samsung
- Sanyo
- Sony

Copyright © 2017 Alpha and Omega Semiconductor. All rights reserved.

Alpha and Omega Semiconductor makes no representations or warranties with respect to the accuracy or completeness of the information provided herein and takes no liabilities for the consequences of use of such information or any product described herein. Alpha and Omega Semiconductor reserves the right to make changes to such information at any time without further notice. This document does not constitute the grant of any intellectual property rights or representation of non-infringement of any third party's intellectual property rights.

CORPORATE OVERVIEW

Alpha and Omega Semiconductor Limited (AOS) is a designer, developer and global supplier of a broad range of power semiconductors, including a wide portfolio of Power MOSFET, IGBT, IPM and Power IC products. AOS has developed extensive intellectual property and technical knowledge that encompasses the latest advancements in the power semiconductor industry, which enables it to introduce innovative products to address the increasingly complex power requirements of advanced electronics. AOS differentiates itself by integrating its Discrete and IC semiconductor process technology, product design, and advanced packaging know-how to develop high-performance power management solutions. AOS' products are aimed at, but not limited to applications such as portable computers, tablets, smart phones, flat panel TVs, LED lighting, battery packs, consumer and industrial motor controls, and power supplies for TVs, computers, servers and telecommunications equipment.



MARKET SEGMENTS

	Computing / Conventional	Computing / Advanced	Consumer	Communications	Industrial / Power Supplies
APPLICATIONS	<ul style="list-style-type: none"> ■ Notebooks ■ Netbooks ■ Desktops ■ NB Battery Packs ■ Game Consoles 	<ul style="list-style-type: none"> ■ Servers ■ Data Storage Devices ■ Ultra Notebooks ■ Tablets ■ Graphic Cards 	<ul style="list-style-type: none"> ■ Quick Charger ■ TV DC-DC Conversion ■ LED Drivers ■ LED Backlighting ■ Home Appliances ■ Induction Heating 	<ul style="list-style-type: none"> ■ Mobile Phones ■ Networking ■ Battery Packs 	<ul style="list-style-type: none"> ■ Motor Controls ■ Power Supplies ■ Telecom Power ■ Lighting ■ Welding ■ PV Inverters
KEY FAMILIES / PLATFORMS	<ul style="list-style-type: none"> ■ Low and Medium Voltage MOSFETs <ul style="list-style-type: none"> - Gen5+ - XSFET™ Family - SGT 	<ul style="list-style-type: none"> ■ Power ICs <ul style="list-style-type: none"> - DC-DC EZBuck™ - DrMOS - Smart Load Management ■ Low and Medium Voltage MOSFETs <ul style="list-style-type: none"> - Gen5+ - XSFET™ Family - SGT 	<ul style="list-style-type: none"> ■ Power ICs <ul style="list-style-type: none"> - DC-DC EZBuck™ - DrMOS - Smart Load Management ■ Low and Medium Voltage MOSFETs <ul style="list-style-type: none"> - Gen5+ - SGT ■ High Voltage MOSFETs <ul style="list-style-type: none"> - 600V α.MOS5™ - 700V ■ IPMs <ul style="list-style-type: none"> - 600V IPM ■ IGBTs <ul style="list-style-type: none"> - 650V IGBT/FRD - 1200V & 1350V IGBT/FRD 	<ul style="list-style-type: none"> ■ Power ICs <ul style="list-style-type: none"> - DC-DC EZBuck™ - DrMOS - Smart Load Management ■ Low and Medium Voltage MOSFETs <ul style="list-style-type: none"> - Gen5+ - XSFET™ Family - SGT 	<ul style="list-style-type: none"> ■ Medium Voltage MOSFETs <ul style="list-style-type: none"> - SGT ■ High Voltage MOSFETs <ul style="list-style-type: none"> - 600V α.MOS5™ - 700V ■ IPMs <ul style="list-style-type: none"> - 600V IPM ■ IGBTs <ul style="list-style-type: none"> - 650V IGBT/FRD



TABLE OF CONTENTS

Power ICs

DC-DC Buck Regulators – Non Synchronous EZBuck™ Family	3
DC-DC Buck Regulators – Synchronous EZBuck™ Family	3
DC-DC Boost Regulators – EZBoost™ Family	7
Power Factor Correction (PFC)	7
Battery Protection ICs	7
DrMOS Power Modules	7
Linear Regulators – LDOs	7
Smart Load Switches – EZPower™ Family	9
Analog Switches	9
High-Speed USB Switches	9

Transient Voltage Suppressors (TVS)

High Current Surge TVS	11
Ultra-Low Capacitance TVS	11
Diode Arrays	13

MOSFETs, IGBTs and IPMs

Low Voltage MOSFETs (<40V) 17

By Package

AlphaDFN™ 0.97x0.97	17
AlphaDFN™ 1.5x1.5 / 1.57x1.57	17
AlphaDFN™ 1.7x1.7	17
AlphaDFN™ 2.7x1.8	17
AlphaDFN™ 3.55x1.77	17
SC-70	17
SC-89	17
SOT-23	17
TSOP-6	19
TSSOP-8	21
DFN 1.0x0.6	21
DFN 1.6x1.6	21
DFN 2x2	21
DFN 2x5	21
DFN 3x2	21
DFN 3x3	21
DFN 3.3x3.3	23
DFN 5x6	25
DFN 5x6 (PairFET™)	27
DFN 5x6E (XSPairFET™)	29
SO-8	29
Ultra SO-8	33
TO-251A	33
TO-251B	33
TO-252	33

Medium Voltage MOSFETs (40V to 400V) 35

By Package

SOT-223	35
SOT-23	35
TSOP-6	35

DFN 2x2	35
DFN 3x3	35
DFN 3.3x3.3	35
DFN 5x6	35
SO-8.....	37
Ultra SO-8	39
TO-220	39
TO-220F	41
TO-247	41
TO-251A.....	43
TO-252	43
TO-262	45
TO-262F	45
TO-263	45
High Voltage MOSFETs.....	49
<i>By Voltage</i>	
V _{DS} = 500V	49
V _{DS} = 600V	49
V _{DS} = 650V	51
α.MOS5™ High Voltage MOSFETs.....	51
<i>By Voltage</i>	
V _{DS} = 600V	51
Planar High Voltage MOSFETs	53
<i>By Voltage</i>	
V _{DS} = 500V	53
V _{DS} = 600V	55
V _{DS} = 650V	57
V _{DS} = 700V and over	59
Intelligent Power Modules (IPMs).....	61
<i>By Package</i>	
DIP	61
Insulated-Gate Bipolar Transistors (IGBTs) – Single.....	61
<i>By Package</i>	
TO-220	61
TO-247	61
Insulated-Gate Bipolar Transistors (IGBTs) – Co-Pack.....	61
<i>By Package</i>	
TO-220	61
TO-220F	61
TO-247	63
TO-252	63
TO-263	63
Package Type	65

POWER ICs

AOS provides best-in-class power management solutions combining Power Discrete and IC technologies. The portfolio of products includes EZBuck™ Step-down DC/DC regulators, EZBoost™ Step-up DC/DC regulators, linear regulators,

DC-DC Buck Regulators – Non Synchronous EZBuck™ Family

Part Number	Description	Integrated Schottky	Soft Start (ms)
AOZ1015AI	1.5A EZBuck Regulator	Yes	Internal - 2.2 ms
AOZ1017AI	3A EZBuck Regulator	No	Internal - 2.2 ms
AOZ1017AIL	3A EZBuck Regulator	No	Internal - 2.2 ms
AOZ1019AI	2A EZBuck Regulator	No	Internal - 4.0 ms
AOZ1056AI	2A EZBuck Regulator	Yes	External - Programmable
AOZ1057AIL	3A EZBuck Regulator	No	External - Programmable
AOZ1083CI	1.2A EZBuck LED Driver	No	Internal - 0.4 ms
AOZ1084DI	1.2A EZBuck LED Driver	No	Internal - 0.6 ms
AOZ1094AIL	5A EZBuck Regulator	No	Internal - 3.0 ms
AOZ1210AI	2A, 4.5 V to 27 V EZBuck Regulator	No	Internal - 4.0 ms
AOZ1212AI	3A, 4.5 V to 27 V EZBuck Regulator	No	Internal - 6.0 ms
AOZ1212DI	3A, 4.5 V to 27 V EZBuck Regulator	No	Internal - 6.0 ms
AOZ1280CI	1.2A, 3 V to 26 V EZBuck Regulator	No	Internal - 0.4 ms
AOZ1281DI	1.8A, 3 V to 26 V EZBuck Regulator	No	Internal - 0.4 ms
AOZ1282CI	1.2A, 4.5 V to 36 V EZBuck Regulator	No	Internal - 1.5 ms
AOZ1282CI-1	600 mA, 4.5 V to 36 V EZBuck Regulator	No	Internal - 0.6 ms
AOZ1282DI	1.2A, 4.5 V to 36 V EZBuck Regulator	No	Internal - 1.5 ms
AOZ1283PI	2.5A, 3 V to 36 V EZBuck Regulator	No	External - Programmable
AOZ1284PI	4A, 3 V to 36 V EZBuck Regulator	No	External - Programmable

DC-DC Buck Regulators – Synchronous EZBuck™ Family

Part Number	Description	PGOOD	Soft Start
AOZ1236QI-01	6 A COT EZBuck Regulator	Yes	Adjustable
AOZ1236QI-02	6 A COT EZBuck Regulator	Yes	Adjustable
AOZ1238QI-01	10 A COT EZBuck Regulator	Yes	Adjustable
AOZ1267QI-01	8 A COT EZBuck Regulator	Yes	Adjustable
AOZ1267QI-02	8 A COT EZBuck Regulator	Yes	Adjustable
AOZ1268QI-01	10 A COT EZBuck Regulator	Yes	Adjustable
AOZ1268QI-02	10A COT EZBuck Regulator	Yes	Adjustable
AOZ1269QI-02	12A COT EZBuck Regulator	Yes	Adjustable

EZPower™ smart load switches, analog switches, and power factor correction (PFC) devices. AOS' approach is to provide high-power density solutions to reduce design complexity and development time.

Min V _{IN} (V)	Max V _{IN} (V)	Max I _{OUT} (A)	Min V _{OUT} (V)	Max V _{OUT} (V)	Operating Freq. (kHz)	Package
4.5	16.0	1.5	0.8	16.0	500	SO-8
4.5	16.0	3.0	0.8	16.0	500	SO-8
4.5	18.0	3.0	0.8	16.0	500	SO-8
4.5	16.0	2.0	0.8	16.0	500	SO-8
4.5	16.0	2.0	0.8	16.0	340	SO-8
4.5	16.0	3.0	0.8	16.0	340	SO-8
3.0	26.0	1.2	0.28	23.8	1500	SOT-23
4.5	36.0	1.2	0.16	30.0	450	DFN 2x2
4.5	16.0	5.0	0.8	16.0	500	SO-8
4.5	27.0	2.0	0.8	23.0	370	SO-8
4.5	27.0	3.0	0.8	23.0	370	SO-8
4.5	27.0	3.0	0.8	23.0	370	DFN 5x4
3.0	26.0	1.2	0.8	26.0	1500	SOT-23
3.0	26.0	1.8	0.8	22.0	1500	DFN 2x2
4.5	36.0	1.2	0.8	36.0	450	SOT-23
4.5	36.0	0.6	0.8	36.0	1000	SOT-23
4.5	36.0	1.2	0.8	36.0	450	DFN 2x2
3.0	36.0	2.5	0.8	30.0	2000	Exposed Pad SO-8
3.0	36.0	4.0	0.8	16.0	2000	Exposed Pad SO-8

Min V _{IN} (V)	Max V _{IN} (V)	Max I _{OUT} (A)	Min V _{OUT} (V)	Max V _{OUT} (V)	Operating Freq. (kHz)	Package
2.7	28.0	6.0	0.8	24.0	1000	QFN 4x4
2.7	24.0	6.0	0.8	20.0	1000	QFN 4x4
2.7	28.0	10.0	0.8	24.0	1000	QFN 4x4
2.7	28.0	8.0	0.8	24.0	1000	QFN 4x4
2.7	24.0	8.0	0.8	20.0	1000	QFN 4x4
6.5	28.0	10.0	0.8	24.0	1000	QFN 4x4
6.5	24.0	10.0	0.8	20.0	1000	QFN 4x4
2.7	28.0	12.0	0.8	24.0	1000	QFN 4x4

DC-DC Buck Regulators – Synchronous EZBuck™ Family

Part Number	Description	PGOOD	Soft Start
AOZ2260QI-10	6A COT EZBuck Regulator	Yes	Adjustable
AOZ2260QI-15	6A COT EZBuck Regulator	Yes	Adjustable
AOZ2261QI-10	8A COT EZBuck Regulator	Yes	Adjustable
AOZ2261QI-11	8A COT EZBuck Regulator	Yes	Adjustable
AOZ2261QI-15	8A COT EZBuck Regulator	Yes	Adjustable
AOZ2262QI-10	10A COT EZBuck Regulator	Yes	Adjustable
AOZ2262QI-15	10A COT EZBuck Regulator	Yes	Adjustable
AOZ2263QI-10	12A COT EZBuck Regulator	Yes	Adjustable
AOZ2263QI-15	12A COT EZBuck Regulator	Yes	Adjustable
AOZ2264QI-10	15A COT EZBuck Regulator	Yes	Adjustable
AOZ3013PI	3A EZBuck with External Soft-Start	No	External - Programmable
AOZ3015PI	3A EZBuck with Light Load Mode	No	Internal - 5.0 ms
AOZ3017PI	4A EZBuck with External Soft-Start	No	External - Programmable
AOZ3024PI	3A EZBuck with Power Good	Yes	Internal - 1.5 ms
AOZ3046PI	4A EZBuck Regulator	No	Internal - 4 ms
AOZ3054DI	6A EZBuck with Smart Mode Adoption	No	Internal - 6 ms
AOZ3101DI	2A EZBuck with Internal Soft-Start	No	Internal - 4 ms
AOZ3103DI	3A EZBuck with Internal Soft-Start	No	Internal - 4 ms
AOZ6605PI	5A EZBuck with External Soft-Start	No	External - Programmable
AOZ6622DI	2A EZBuck with Internal Soft-Start/Compensation	No	Internal - 1.5 ms
AOZ6623DI	3A EZBuck with Internal Soft-Start/Compensation	No	Internal - 1.5 ms
AOZ6643DI	3A EZBuck with Internal Soft-Start	No	Internal - 4 ms

Min V _{IN} (V)	Max V _{IN} (V)	Max I _{OUT} (A)	Min V _{OUT} (V)	Max V _{OUT} (V)	Operating Freq. (kHz)	Package
2.7	28.0	6.0	0.8	24.0	1000	QFN 4x4
2.7	28.0	6.0	0.8	24.0	1000	QFN 4x4
2.7	28.0	8.0	0.8	24.0	1000	QFN 4x4
2.7	28.0	8.0	0.8	24.0	1000	QFN 4x4
2.7	28.0	8.0	0.8	24.0	1000	QFN 4x4
2.7	28.0	10.0	0.8	24.0	1000	QFN 4x4
2.7	28.0	10.0	0.8	24.0	1000	QFN 4x4
2.7	28.0	12.0	0.8	24.0	1000	QFN 4x4
2.7	28.0	12.0	0.8	24.0	1000	QFN 4x4
2.7	24.0	15.0	0.8	20.0	1000	QFN 4x4
4.5	18.0	3.0	0.8	15.3	500	Exposed Pad SO-8
4.5	18.0	3.0	0.8	15.3	500	Exposed Pad SO-8
4.5	18.0	4.0	0.8	15.3	500	Exposed Pad SO-8
4.5	18.0	3.0	0.8	15.3	500	Exposed Pad SO-8
7.5	18.0	4.0	0.8	15.3	500	Exposed Pad SO-8
4.5	18.0	5.0	0.8	15.3	500	DFN 5x6
4.5	18.0	2.0	0.8	15.3	500	DFN 3x3
4.5	18.0	3.0	0.8	15.3	500	DFN 3x3
4.5	18.0	5.0	0.6	15.3	650	Exposed Pad SO-8
4.5	18.0	2.0	0.8	15.3	550	DFN 3x3
4.5	18.0	3.0	0.8	15.3	550	DFN 3X3
4.5	18.0	3.0	0.8	15.3	500	DFN 3X3

DC-DC Boost Regulators – EZBoost™ Family

Part Number	Description	Integrated Schottky
AOZ1905DI	2.7V to 5.5V EZBoost Regulator	No
AOZ1915DI	2.7V to 5.5V EZBoost Regulator	No
AOZ1977AI	High Voltage Boost LED Driver Controller	No
AOZ1977AI-1	High Voltage Boost LED Driver Controller	No
AOZ1978AI	High Voltage Boost LED Driver Controller	No

Power Factor Correction (PFC)

Part Number	Description	PFC Mode	Freq. Operation	Control Mode
AOZ7111AI	Critical Conduction Mode PFC Controller	CRM	Variable	Voltage

Battery Protection ICs

Part Number	Overcharge Detection Voltage (V_{CU}) (V)	Overcharge Release Voltage (V_{CL}) (V)	Overdischarge Detection Voltage (V_{DL}) (V)	Overdischarge Release Voltage (V_{DU}) (V)
AOZ9250DI	4.375	4.175	2.8	2.8
AOZ9252DI	4.225	4.025	2.8	2.8
AOZ9256DI	4.375	4.175	2.8	2.8

DrMOS Power Modules

Part Number	Min V_{IN} (V)	Max V_{IN} (V)	Max Current (A)	PWM Logic (V)	Package	
AOZ5019QI	4.5	25.0	30.0	5.0	QFN 3.5x5	
AOZ5036QI-01	4.5	16.0	60.0	3.3	QFN 6x6	
AOZ5049QI	4.5	25.0	35.0	5.0	QFN 3.5x5	
AOZ5066QI	4.5	25.0	60.0	5.0	QFN 6x6	
AOZ5066QI-01	4.5	25.0	60.0	3.3	QFN 6x6	
AOZ5131QI	NEW	4.5	18.0	60.0	5.0	QFN 5x5
AOZ5166QI-01	4.5	25.0	60.0	3.3	QFN 6x6	
AOZ5039QI	4.5	25.0	50.0	5.0	QFN 5x5	
AOZ5038QI	4.5	25.0	60.0	5.0	QFN 5x5	
AOZ5048QI	4.5	25.0	35.0	5.0	QFN 5x5	
AOZ5239QI	NEW	4.5	25.0	70.0	3.3 / 5.0	QFN 5x5

Linear Regulators – LDOs

Part Number	Min V_{IN} (V)	Max V_{IN} (V)	Min V_{OUT} (V)	Max I_{OUT} (A)	Dropout Voltage	Package
AOZ2023PI	1.3	5.5	3.0	0.8	180mV @ 2A	Exposed Pad SO-8

Min V_{IN} (V)	Max V_{IN} (V)	I _{sw} SWITCH CURRENT LIMIT (A)	Min V_{OUT} (V)	Max V_{OUT} (V)	Operating Freq. (kHz)	Package
2.7	5.5	2	V _{in} *1.2	24.0	600kHz / 1.2MHz	DFN 3x3
2.7	5.5	2	V _{in} *1.2	24.0	600kHz / 1.2MHz	DFN 4x3
8.0	N/A	N/A	N/A	N/A	Adjustable	SO-16
8.0	N/A	N/A	N/A	N/A	Adjustable	SO-16
8.0	N/A	N/A	N/A	N/A	200	SO-20

Topology	Max Freq. Limit (Typ.) KHz	V _{CC} Max (V)	Drive Capability (mA)	ULVO (V)	OVP Latch	Min On-Time (Typ.) ns	Package
Step-up	350	20.0	+300/-800	9.5-12	Yes	450	SO-8

Overdischarge Release Voltage (V _{DU2}) (V)	Discharge Overcurrent Threshold (V _{DIOV}) (V)	Load Shortcircuiting Detection (V _{SHORT}) (V)	Charge Overcurrent Threshold (V _{CIOV}) (V)	R _{SS} @ 3.9V mΩ	Package
2.41	0.11	0.5	-0.1	24.4	DFN 2x4
2.41	0.14	0.5	-0.15	24.4	DFN 2x4
2.41	0.13	0.5	-0.125	24.4	DFN 2x4

Smart Load Switches – EZPower™ Family

Part Number	Description	V _{IN} (V)	Turn On Rise Time (T _r)
AOZ1310CI-1	Single USB Load Switch	2.7 - 5.5	1.5ms
AOZ1312AI-1	Single USB Load Switch	2.7 - 5.5	1.5ms
AOZ1312EI-1	Single USB Load Switch	2.7 - 5.5	1.5ms
AOZ1320CI	Slew Rate Controlled Smart Load Switch	1.8 - 5.5	100 μs, 0.5 μs, 1.0 ms
AOZ1320DI	Slew Rate Controlled Smart Load Switch	1.8 - 5.5	100 μs, 0.5 μs, 1.0 ms
AOZ1321DI	Slew Rate Controlled Smart Load Switch	1.6 - 5.5	1.0 μs, 100 μs, 800 μs
AOZ1360AI	EZPower™ Protected Smart Load Switch	5.5 - 28	Adjustable
AOZ1360DI	EZPower™ Protected Smart Load Switch	5.5 - 28	Adjustable
AOZ1361DI-01	EZPower™ Protected Smart Load Switch	5.5 - 28	Adjustable
AOZ1361DI-02	EZPower™ Protected Smart Load Switch	5.5 - 28	Adjustable
AOZ1363DI	EZPower™ Protected Smart Load Switch	5.0 - 16	16 μs
AOZ1334DI-01	Single Channel Smart Load Switch	0.8 - 5.5	10 μs
AOZ1334DI-02	Single Channel Smart Load Switch	0.8 - 5.5	0.5ms
AOZ1336DI	Single Channel Smart Load Switch	0.8 - 5.5	Adjustable
AOZ1325DI	Dual Slew Rate Controlled Smart Load Switch	1.6 - 5.5	1.0ms
AOZ1331DI	Dual Channel Smart Load Switch	0.8 - 5.5	Adjustable
AOZ1341AI	Dual USB Load Switch	2.7 - 5.5	1.5ms
AOZ1341EI	Dual USB Load Switch	2.7 - 5.5	1.5ms
AOZ1342PI	Dual USB Load Switch	2.7 - 5.5	1.5ms
AOZ1342PI-1	Dual USB Load Switch	2.7 - 5.5	1.5ms
AOZ1375DI-01	NEW ECPower™ Bidirectional Load Switch	3.4 - 23	Adjustable
AOZ1375DI-02	NEW ECPower™ Bidirectional Load Switch	3.4 - 23	Adjustable

Analog Switches

Part Number	Description	On Resistance R _{ON} (Typ.) at 2.7 V	On Resistance Flatness RFLAT _(ON) (Max) at 2.7 V
AOZ6115CI	Single SPST	2.0 Ω at 4.5 V	0.25 Ω at 4.5 V
AOZ6115HI	Single SPST	2.0 Ω at 4.5 V	0.25 Ω at 4.5 V
AOZ6134DI	Single SPDT	0.6 Ω at 4.5 V	0.25 Ω at 4.5 V
AOZ6135HI	Single SPDT	0.9 Ω at 4.5 V	0.25 Ω at 4.5 V
AOZ6232QI	Dual SPDT	0.25 Ω	0.15 Ω
AOZ6233QI	Dual SPDT	0.35 Ω	0.15 Ω
AOZ6234QI	Dual SPDT	0.40 Ω	0.15 Ω
AOZ6236QI	Dual SPDT	0.40 Ω	0.15 Ω
AOZ6274QI	Dual DPDT	0.40 Ω	0.15 Ω
AOZ6275QI	Dual DPDT	0.35 Ω	0.25 Ω

High-Speed USB Switches

Part Number	Description	On Resistance R _{ON} (Typ.) at 3.6 V	On Capacitance C _(ON) (Typ.) at 3.3 V
AOZ6184QT	High Speed (USB2.0) DPDT; Bandwidth 1.1 GHz	8.0 Ω	3.6 Ω
AOZ6185QT	High Speed (USB2.0) DPDT w/Flat R _{ON} Bandwidth 990 MHz	7.2 Ω	1.9 Ω
AOZ6186QT	High Speed (USB2.0) DPDT; Bandwidth 960 MHz	7.0 Ω	5.0 Ω

Channel	Enable	Current Limit (A)	Fault Latch	R _{DS(ON)} (mΩ) (Typ)	Package
1	Active High	0.75	Yes	80	SOT-23
1	Active High	2.0	Yes	70	SO-8
1	Active High	2.0	Yes	70	Exposed Pad MSOP
1	CMOS/TTL Compatible	No	Yes	75	SOT-23
1	CMOS/TTL Compatible	No	Yes	75	DFN 2x2
1	CMOS/TTL Compatible	No	Yes	60	DFN 1.2x1.6
1	CMOS/TTL Compatible	Adjustable	Yes	35	SO-8
1	CMOS/TTL Compatible	Adjustable	Yes	35	DFN 4x4
1	CMOS/TTL Compatible	Adjustable	No	35	DFN 4x4
1	CMOS/TTL Compatible	Adjustable	Yes	35	DFN 4x4
1	CMOS/TTL Compatible	11.0	Yes	23	DFN 3x3
1	CMOS/TTL Compatible	10.0	No	5	DFN 3x3
1	CMOS/TTL Compatible	10.0	No	5	DFN 3x3
1	CMOS/TTL Compatible	4.0	No	27	DFN 2x2
2	CMOS/TTL Compatible	No	Yes	150	DFN 3x3
2	CMOS/TTL Compatible	6.0	No	20	DFN 3x2
2	CMOS/TTL Compatible	1.5	Yes	70	SO-8
2	CMOS/TTL Compatible	1.5	Yes	70	Exposed Pad MSOP
2	Active Low	2.0	Yes	70	Exposed Pad SO-8
2	Active High	2.0	Yes	70	Exposed Pad SO-8
1	CMOS/TTL Compatible	Adjustable	No	18	DFN 3x3
1	CMOS/TTL Compatible	Adjustable	Yes	18	DFN 3x3

Supply Voltage Range V _{CC} (V)	Total Harmonic Distortion THD (Typ.) (%)	Package
1.65 to 5.5	0.005 %	SOT-23
1.65 to 5.5	0.005 %	SC-70
1.65 to 5.5	0.002 %	DFN 1.2x1.0
1.65 to 5.5	0.005 %	SC-70
1.65 to 3.3	0.024 %	QFN 2.1x1.6
1.65 to 3.3	0.024 %	QFN 2.1x1.6
1.65 to 3.3	0.024 %	QFN 2.1x1.6
1.65 to 4.3	0.010 %	QFN 1.8x1.4
1.65 to 4.3	0.024 %	QFN 3x3
1.65 to 4.3	0.01 %	QFN 1.8x2.6

Supply Voltage Range V _{CC} (V)	-dB Bandwidth Hz (Typ.)	Package
1.65 to 4.5	1.1 G	QFN 1.8x1.4
1.65 to 4.5	990 M	QFN 1.8x1.4
1.65 to 4.5	960 M	QFN 1.8x1.4

TRANSIENT VOLTAGE SUPPRESSORs (TVS)

AOS provides a family of high current surge and ultra-low capacitance Transient Voltage Suppressor (TVS), and Diode Array-Thunderbolt, SATA and Gigabit Ethernet ports. These products may be used to meet the ESD immunity requirement

High Current Surge TVS

Part Number	Description	IEC 61000-4-2 (ESD)		Protected Lines
		Contact (kV)	Air (kV)	
AOZ8202ACI-12	1-Line Bidirectional TVS Diode	± 30	± 30	1
AOZ8302ACI-05	2-Line TVS Diode Array	± 30	± 30	2
AOZ8302ACI-12	2-Line TVS Diode Array	± 30	± 30	2
AOZ8300CI-03	Ultra-Low Capacitance TVS Diode Array	± 30	± 30	4
AOZ8300CI-05	Ultra-Low Capacitance TVS Diode Array	± 30	± 30	4
AOZ8309	Ultra-Low Capacitance TVS Diode Array	± 30	± 30	4
AOZ8318DI	Ultra-Low Capacitance TVS Diode Array	± 30	± 30	4
AOZ8328DI	Ultra-Low Capacitance TVS Diode Array	± 30	± 30	4
AOZ8915CI	Ultra-Low Capacitance TVS Diode Array	± 24	± 30	4

Ultra-Low Capacitance TVS

Part Number	Description	IEC 61000-4-2 (ESD)		Protected Lines
		Contact (kV)	Air (kV)	
AOZ8001DI	Ultra-Low Capacitance TVS Diode Array	± 8	± 15	2
AOZ8101	Ultra-Low Capacitance TVS Diode Array	± 30	± 30	2
AOZ8802ADI	Ultra-Low Capacitance TVS Diode Array	± 15	± 15	2
AOZ8881DI-05	Ultra-Low Capacitance TVS Diode Array	± 15	± 15	2
AOZ8882DI-05	Ultra-Low Capacitance TVS Diode Array	± 15	± 15	2
AOZ8000CI	Ultra-Low Capacitance TVS Diode Array	± 8	± 15	4
AOZ8102DI	Ultra-Low Capacitance TVS Diode Array	± 20	± 20	4
AOZ8106CI	Ultra-Low Capacitance TVS Diode Array w/ Blocking Diode	± 24	± 30	4
AOZ8132ADI	Ultra-Low Capacitance TVS Diode Array	± 20	± 20	4
AOZ8804ADI	Ultra-Low Capacitance TVS Diode Array	± 15	± 15	4
AOZ8808DI-03	Ultra-Low Capacitance TVS Diode Array	± 15	± 15	4
AOZ8808DI-05	Ultra-Low Capacitance TVS Diode Array	± 15	± 15	4
AOZ8809DI-03	Ultra-Low Capacitance TVS Diode Array	± 15	± 15	4
AOZ8809DI-05	Ultra-Low Capacitance TVS Diode Array	± 15	± 15	4
AOZ8809ADI-03	NEW Ultra-Low Capacitance TVS Diode Array	± 15	± 15	4
AOZ8809ADI-05	NEW Ultra-Low Capacitance TVS Diode Array	± 15	± 15	4
AOZ8829DI-03	Ultra-Low Capacitance TVS Diode Array	± 30	± 30	4
AOZ8844DT-05	Ultra-Low Capacitance TVS Diode Array	± 15	± 20	4
AOZ8903CI	Ultra-Low Capacitance TVS Diode Array	± 15	± 20	4
AOZ8904CIL	Ultra-Low Capacitance TVS Diode Array	± 24	± 24	4
AOZ8905CI	Ultra-Low Capacitance TVS Diode Array	± 8	± 15	4
AOZ8906CI	Ultra-Low Capacitance TVS Diode Array	± 15	± 20	4
AOZ8806DI-03	Ultra-Low Capacitance TVS Diode Array	± 15	± 15	6
AOZ8806DI-05	Ultra-Low Capacitance TVS Diode Array	± 15	± 15	6

of products that are designed for ESD protection of high-speed interfaces like HDMI2.0, USB3.1, IEEE1394, IEC61000-4-2, Level 4 for mobile, digital consumer, networking, and computing applications.

Reverse Working Voltage V_{RWM} Max (V)	IEC 61000-4-5 (Lightning) (A)	Channel Input Capacitance I/O - GND Typ. (pF)	Channel Clamp Voltage (Ipp = 5A) V_{CL} Max. (V)	Package
12.0	15	62	19.0	SOT-23
5.0	32	20	14.0 (Ipp = 15A)	SOT-23
12.0	24	20	179.0 (Ipp = 15A)	SOT-23
3.3	25	2.5	2.6	SOT-23
2.5	20	2.5	3.5	SOT-23
3.3	16	2.5	5.9 (Ipp = 16A)	DFN 2.5x1.0
2.5	25	3.5	3.5	DFN 2.6x2.6
2.5	32	2.8	4.5	DFN 3.0x2.0
5.0	12	0.5	12.0	SOT-23

Reverse Working Voltage V_{RWM} Max (V)	Channel Input Capacitance		Channel Clamp Voltage (Ipp = 5A) V_{CL} Max. (V)	Package
	I/O - I/O Typ. (pF)	I/O - GND Typ. (pF)		
5.5	0.9	1.0	11.0	DFN 1.6x1.6
5.5	0.7	1.3	2.4	SOT-23
5.0	0.3	0.6	16.5	DFN 1.6x1.0
5.0	0.3	0.3	20.0	DFN 1.2x1.1
5.0	0.3	0.3	12.0	DFN 1.2x1.1
5.5	0.9	1.0	11.0	SOT-23
5.5	0.9	1.0	12.0	DFN 1.6x1.6
5.5	0.43	0.8	16.0	SOT-23
5.0	0.6	—	7.0	DFN 1.6x1.6
5.0	0.3	0.6	16.5	DFN 2.5x1.0
3.3	0.3	0.6	5.0	DFN 2.5x1.0
5.0	0.3	0.6	6.0	DFN 2.5x1.0
3.3	0.2	0.45	5.0	DFN 2.5x1.0
5.0	0.2	0.45	6.0	DFN 2.5x1.0
3.3	0.2	0.45	4.0	DFN 2.5x1.0
5.0	0.2	0.45	5.0	DFN 2.5x1.0
3.3	0.25	0.6	3.0	DFN 2.5x1.0
5.0	0.25	0.5	6.5	DFN 1.3x0.8
5.5	0.25	0.5	4.5	SOT-23
5.5	0.9	1.25	14.0	SOT-23
5.0	0.35	0.7	22.0	SOT-23
5.5	0.35	0.5	4.0	SOT-23
3.3	0.3	0.6	16.5	DFN 3.3x1.3
5.0	0.3	0.6	16.5	DFN 3.3x1.3

Ultra-Low Capacitance TVS (Continued)

Part Number	Description	IEC 61000-4-2 (ESD)		Protected Lines
		Contact (kV)	Air (kV)	
AOZ8807DI-03	Ultra-Low Capacitance TVS Diode Array	± 15	± 15	6
AOZ8807DI-05	Ultra-Low Capacitance TVS Diode Array	± 15	± 15	6
AOZ8312DI	Ultra-Low Capacitance TVS Diode Array	± 30	± 30	12

Diode Arrays

Part Number	Description	IEC 61000-4-2 (ESD)		Protected Lines
		Contact (kV)	Air (kV)	
AOZ8131DI	Ultra-Low Capacitance Bidirectional Single Diode	± 24	± 24	1
AOZ8211DI-02	Low Capacitance Unidirectional Single Diode	± 30	± 30	1
AOZ8211DI-03	Low Capacitance Unidirectional Single Diode	± 30	± 30	1
AOZ8211DI-05	Low Capacitance Unidirectional Single Diode	± 28	± 28	1
AOZ8211DI-12	Low Capacitance Unidirectional Single Diode	± 28	± 28	1
AOZ8211DI-24	Low Capacitance Unidirectional Single Diode	± 18	± 15	1
AOZ8231ADI-02	Low Capacitance Bidirectional Single Diode	± 30	± 30	1
AOZ8231ADI-03	Low Capacitance Bidirectional Single Diode	± 30	± 30	1
AOZ8231ADI-05	Low Capacitance Bidirectional Single Diode	± 30	± 30	1
AOZ8231ADI-08	Low Capacitance Bidirectional Single Diode	± 30	± 30	1
AOZ8231ADI-12	Low Capacitance Bidirectional Single Diode	± 30	± 30	1
AOZ8231ADI-24	Low Capacitance Bidirectional Single Diode	± 15	± 18	1
AOZ8231BDI-08	Low Capacitance Bidirectional Single Diode	± 18	± 18	1
AOZ8251ADI-02	1-Line Bidirectional TVS Diode	± 30	± 20	1
AOZ8251ADI-03	1-Line Bidirectional TVS Diode	± 20	± 20	1
AOZ8251ADI-05	1-Line Bidirectional TVS Diode	± 20	± 20	1
AOZ8251BDI-05	NEW 1-Line Bidirectional TVS Diode	± 20	± 20	1
AOZ8251BDI-12	NEW 1-Line Bidirectional TVS Diode	± 20	± 20	1
AOZ8811DI	Ultra-Low Capacitance Single Diode	± 8	± 15	1
AOZ8811DT-03	Ultra-Low Capacitance Single Diode	± 20	± 20	1
AOZ8821DI-05	Ultra-Low Capacitance Single Diode	± 15	± 15	1
AOZ8821DT-03	Ultra-Low Capacitance Single Diode	± 20	± 20	1
AOZ8831ADI-05	Ultra-Low Capacitance TVS Diode	± 25	—	1
AOZ8831DI-05	Ultra-Low Capacitance Bidirectional Single Diode	± 15	± 15	1
AOZ8831DT-03	Ultra-Low Capacitance Bidirectional Single Diode	± 20	± 20	1
AOZ8831DT-05	Ultra-Low Capacitance Bidirectional Single Diode	± 20	± 20	1
AOZ8831DT-24	Ultra-Low Capacitance Bidirectional Single Diode	± 15	± 13	1
AOZ8841DI-05	Ultra-Low Capacitance Bidirectional Single Diode	± 25	± 15	1
AOZ8851ADI-03	Ultra-Low Capacitance Bidirectional Single Diode	± 20	± 20	1
AOZ8851ADI-05	Ultra-Low Capacitance Bidirectional Single Diode	± 20	± 20	1
AOZ8212ACI-05	Low Capacitance Bidirectional Diode Arrays	± 15	± 15	2
AOZ8212BCI-12	Low Capacitance Bidirectional Diode Arrays	± 30	± 30	2
AOZ8212BCI-24	Low Capacitance Bidirectional Diode Arrays	± 15	± 18	2
AOZ8222DI-05	2-Line TVS Diode	± 20	± 20	2
AOZ8822DI-05	Low Capacitance 2-Line Diode	± 15	± 15	2
AOZ8832DI-05	Low Capacitance Bidirectional 2-Line Diode	± 12	± 12	2
AOZ8204DI	Low Capacitance Diode Arrays	± 30	± 30	4
AOZ8224CI-05	Low Capacitance Bidirectional Diode Arrays	± 30	± 30	4

Reverse Working Voltage V_{RWM} Max (V)	Channel Input Capacitance		Channel Clamp Voltage ($I_{pp} = 5A$) V_{CL} Max. (V)	Package
	I/O - I/O Typ. (pF)	I/O - GND Typ. (pF)		
3.3	0.2	0.45	10.0	DFN 3.3x1.3
5.0	0.2	0.45	11.0	DFN 3.3x1.3
2.5	1.2	2.3	5.0	DFN 3.5x2.5

Reverse Working Voltage V_{RWM} Max (V)	Channel Input Capacitance I/O - GND Typ. (pF)	Channel Clamp Voltage ($I_{pp} = 15A$) V_{CL} Max. (V)	Package
5.0	1.25	20.0	DFN 1.0x0.6
2.5	11.0	9.5	DFN 1.0x0.6
3.3	11.0	10.0	DFN 1.0x0.6
5.0	16.0	10.0	DFN 1.0x0.6
12.0	30.0	21.0	DFN 1.0x0.6
24.0	20.0	37.0	DFN 1.0x0.6
2.5	5.5	13.0	DFN 1.0x0.6
3.3	5.5	14.0	DFN 1.0x0.6
5.0	13.0	16.0	DFN 1.0x0.6
8.0	23.0	23.0	DFN 1.0x0.6
12.0	13.0	27.0	DFN 1.0x0.6
24.0	12.0	39.0	DFN 1.0x0.6
8.0	45.0	18.0	DFN 1.0x0.6
2.5	10.0	15.0	DFN 0.6x0.3
3.3	10.0	16.0	DFN 0.6x0.3
5.0	10.0	17.0	DFN 0.6x0.3
5.0	5.0	16.5	DFN 0.62x0.32
12.0	4.5	25V	DFN 0.62x0.32
5.0	0.50	23.0	DFN 1.0x0.6
3.6	—	—	DFN 1.0x0.6
5.0	0.65	15.0	DFN 1.0x0.6
3.6	—	—	DFN 1.0x0.6
5.0	0.3	19.0	DFN 1.6x1.0
5.0	0.35	23.0	DFN 1.0x0.6
3.6	0.22	15.0	DFN 1.0x0.6
5.0	0.22	15.0	DFN 1.0x0.6
24.0	0.35	48.0	DFN 1.0x0.6
5.0	0.30	19.5	DFN 1.0x0.6
3.3	0.22	16.0	DFN 0.62x0.32
5.0	0.22	17.0	DFN 0.62x0.32
5.0	11.0	16.0	SOT-23
12.0	10.0	24.0	SOT-23
24.0	11.0	40.0	SOT-23
5.0	15.0	10.0	DFN 1.0x0.6
5.0	0.55	17.0	DFN 1.0x0.6
5.0	0.4	19.5	DFN 1.0x0.6
5.0	17.0	7.0	DFN 1.6x1.6
5.0	13.0	18.0	SOT-23

Diode Arrays (Continued)

Part Number	Description	IEC 61000-4-2 (ESD)		Protected Lines
		Contact (kV)	Air (kV)	
AOZ8234DI	Low Capacitance 4-Line Diode Array	± 18	± 18	4
AOZ8244DI-05	Low Capacitance Bidirectional Diode Arrays	± 18	± 18	4
AOZ8858DI-03	NEW Ultra-Low Capacitance Diode Array	± 30	± 30	4
AOZ8245DI	Low Capacitance Bidirectional Diode Arrays	± 20	± 20	5
AOZ8205DI	Low Capacitance Diode Arrays	± 30	± 30	5
AOZ8235DI	Low Capacitance 5-Line Diode Array	± 18	± 18	5
AOZ8236DI-05	5-Line TVS Diode Array	± 30	± 30	5
AOZ8206DI	Low Capacitance Diode Arrays	± 20	± 20	6
AOZ8208DI	Low Capacitance Diode Arrays	± 28	± 28	8

Reverse Working Voltage V_{RWM} Max (V)	Channel Input Capacitance I/O - GND Typ. (pF)	Channel Clamp Voltage ($I_{pp} = 15A$) V_{CL} Max. (V)	Package
5.0	13.5	12.0	DFN 1.45x1.0
5.0	0.5	20.0	DFN 1.45x1.0
3.3	0.25	10.0	DFN 1.45x1.0
3.3	0.25	10.0	DFN 1.45x1.0
5.0	17.0	7.0	DFN 1.6x1.6
5.0	13.5	12.0	DFN 1.45x1.0
5.0	—	13.5	DFN 1.6x1.6
5.0	17.0	9.0	DFN 1.6x1.6
5.0	17.0	9.0	DFN 1.8x1.2

MOSFETs, IGBTs AND IPMs

AOS pioneered the fab-lite model in the Trench Power MOSFET field, developing leading-edge products that are exclusively manufactured in state-of-the-art 8-inch fabs. Advanced proprietary silicon and packaging processes are designed in AOS' U.S.

Low Voltage MOSFETs

Part Number	Package	Configuration	Popular Application	Type	ESD Diode	Schottky Diode	Schottky Type	V _{DS} (V)	V _{GS} (±V)
AlphaDFN™ 0.97x0.97									
AOC2421	MCSP 0.97x0.97A	Single	Load Switch	P	Yes	No		-8	5
AlphaDFN™ 1.5x1.5/1.57x1.57									
AOC2804B	MCSP 1.5x1.5	Common Drain	Load Switch	N	Yes	No		20	12
AlphaDFN™ 1.7x1.7									
AOC2870	MCSP 1.7x1.7	Common Drain	Load Switch	N	Yes	No		20	12
AOC2806	MCSP 1.7x1.7	Common Drain	Load Switch	N	Yes	No		20	12
AlphaDFN™ 2.7x1.8									
AOC3864	MCSP 2.7x1.8	Common Drain	Load Switch	N	Yes	No		20	8
AOC3868	MCSP 2.7x1.8	Common Drain	Load Switch	N	Yes	No		12	8
AlphaDFN™ 3.55x1.77									
AOC3860	MCSP 3.05x1.77	Common Drain	Load Switch	N	Yes	No		12	8
AOC3862	MCSP 3.55x1.77	Common Drain	Load Switch	N	Yes	No		12	8
SC-70									
AO7400	SC-70-3	Single	General Purpose	N	No	No		30	12
AO7410	SC-70-3	Single	General Purpose	N	No	No		30	12
AO7412	SC-70-6	Single	General Purpose	N	No	No		30	12
AO7408	SC-70-6	Single	General Purpose	N	No	No		20	8
AO7414	SC-70-6	Single	General Purpose	N	No	No		20	8
AO7407	SC-70-3	Single	General Purpose	P	No	No		-20	8
AO7411	SC-70-6	Single	General Purpose	P	No	No		-20	8
AO7413	SC-70-3	Single	General Purpose	P	Yes	No		-20	12
AO7415	SC-70-6	Single	General Purpose	P	Yes	No		-20	12
AO7417	SC-70-6	Single	General Purpose	P	No	No		-20	8
AO7401	SC-70-3	Single	General Purpose	P	No	No		-30	12
AO7405	SC-70-6	Single	General Purpose	P	No	No		-30	12
AO7800	SC-70-6	Dual	General Purpose	N	Yes	No		20	8
AO7801	SC-70-6	Dual	General Purpose	P	No	No		-20	8
SC-89									
AO5401E	SC-89-3	Single	Load Switch	P	Yes	No		-20	8
AO5803E	SC-89-6	Dual	Load Switch	P	Yes	No		-20	8
AO5600E	SC-89-6	Complementary	Inverter	N	Yes	No		20	8
AO5600E	SC-89-6	Complementary	Inverter	P	Yes	No		-20	8
SOT-23									
AO3400	SOT-23-3	Single	General Purpose	N	No	No		30	12
AO3400A	SOT-23-3	Single	General Purpose	N	No	No		30	12
AO3402	SOT-23-3	Single	General Purpose	N	No	No		30	12
AO3404	SOT-23-3	Single	General Purpose	N	No	No		30	20
AO3404A	SOT-23-3	Single	General Purpose	N	No	No		30	20

1. Not recommended for new designs. Please contact your local sales office for a replacement part, if any.
 2. On-resistance Static Source-Source, otherwise Static Drain-Source.

headquarters and are then produced with its very efficient manufacturing model. Our product portfolio covers 6V to 1000V MOSFETs; 600V, 650V, 1200V, and 1350V IGBTs and 600V 3-phase motor drives IPMs.

I _D (A)		P _D (W)		R _{DS(ON)} (mΩ max) at V _{GS} =						V _{GS(th)}	C _{iss}	C _{oss}	C _{rss}	Q _g	Q _{gd}	T _{rr}	Q _{rr}
25°C	70°C	25°C	70°C	10V	4.5V	2.5V	1.8V	1.5V	1.2V	(max V)	(pF)	(pF)	(pF)	(nC)	(nC)	(ns)	(nC)
-2.5		0.6				60	72	85	115	-0.7	752	178	104	7.5	1	12	4
6		1.3			34 ⁽²⁾	56 ⁽²⁾				1.3				9.5			
10		1.4			11.9	20				1.3				11.5			
4.5		0.7			18 ⁽²⁾	29 ⁽²⁾				0.85				12.5			
19		2.4			5.7 ⁽²⁾	9 ⁽²⁾				1.3				27			
20		2.5			5	7				1.1				35			
30		2.5			2.7	4.2				0.9				44			
27		2.5			3.0	4.4				1.2				46			
1.7	1.3	0.35	0.22	55	65	85				1.5	235	35	18	4.7	1.6	8.5	2.6
1.7	1.3	0.35	0.22	55	65	85				1.5	235	35	18	4.7	1.6	8.5	2.6
1.7	1.3	0.35	0.22	55	65	85				1.5	235	35	18	4.7	1.6	8.5	2.6
2	1.5	0.35	0.22		62	75	85			1	260	48	27	2.9*	0.6	14	3.8
2	1.5	0.35	0.22		62	70	85			1	260	48	27	2.9	0.6	14	3.4
-1.2	-1	0.63	0.4		135	170	220			-1	560	80	70	8.5*	2.1	37	27
-1.8	-1.5	0.63	0.4		120	150	200			-1	560	80	70	8.5	2.1	37	27
-1.4	-1.2	0.35	0.22	113	135	180				-1.2	325	63	37	3.2	0.9	6.1	1.4
-2	-1.6	0.63	0.4	100	125	170				-1.2	325	63	37	3.2	0.9	6.1	1.4
-1.9	-1.6	0.57	0.36		80	100	125	150		-1	560	80	70	8.5	2.1	37	27
-1.4	-1	0.35	0.22	115	140	200				-1.4	260	37	20	2.8	1	11.5	4.5
-1.4	-1	0.35	0.22	115	140	200				-1.4	260	37	20	2.8	1	11.5	4.5
0.9	0.7	0.3	0.19		300	350	450			0.9	101	17	14	1.57	0.36	6.7	1.6
-0.6	-0.48	0.3	0.19		520	700	950			-0.9	114	17	14	1.44	0.35	10	3
-0.5	-0.45	0.38	0.24		800	1000	1300			-0.9	72	17	9			27	8.3
-0.6	-0.4	0.4	0.24		800	1000	1250			-0.9	72	17	9			27	8.3
0.6	0.4	0.38	0.24		650	750	950			1	35	8	6	0.63	0.16	8	2
-0.5	-0.4	0.38	0.24		800	1000	1300			-1	72	17	9			27	8.3
5.8	4.9	1.4	1	28	33	52				1.45	630	75	50	6	1.8	8.5	2.6
5.7	4.7	1.4	0.9	26.5	32	48				1.45	630	75	50	6	1.8	8.5	2.6
4	3.2	1.4	0.9	52	65	85				1.5	235	35	18	4.7	1.6	8.5	2.6
5	4	1.4	0.9	31	43					2.4	255	45	35	2.55	1.3	8.5	2.2
5.8	4.9	1.4	0.9	25	35					2.6	373	67	41	3.3	1.7	10.5	4.5

* For bottom exposed packages, the I_D and P_D are calculated at 100°C, otherwise at 70°C.

* R_{DS(ON)} measured at V_{GS} other than 10V, 4.5V, 1.8V, 1.5V, or 1.2V.

* Q_g measured with V_{GS} = 10V. In all other cases V_{GS} = 4.5V.

Low Voltage MOSFETs (Continued)

Part Number	Package	Configuration	Popular Application	Type	ESD Diode	Schottky Diode	Schottky Type	V _{DS} (V)	V _{GS} (±V)
AO3406	SOT-23-3	Single	General Purpose	N	No	No		30	20
AO3418	SOT-23-3	Single	SMPS	N	No	No		30	12
AO3424	SOT-23-3	Single	General Purpose	N	No	No		30	12
AO3434A	SOT-23-3	Single	Battery Protection	N	Yes	No		30	12
AO3414	SOT-23-3	Single	General Purpose	N	No	No		20	8
AO3416	SOT-23-3	Single	Load Switch	N	Yes	No		20	8
AO3420	SOT-23-3	Single	Load Switch	N	No	No		20	12
AO3413	SOT-23-3	Single	General Purpose	P	No	No		-20	8
AO3415	SOT-23-3	Single	General Purpose	P	Yes	No		-20	8
AO3415A	SOT-23-3	Single	General Purpose	P	Yes	No		-20	8
AO3419	SOT-23-3	Single	General Purpose	P	Yes	No		-20	12
AO3423	SOT-23-3	Single	General Purpose	P	Yes	No		-20	12
AO3435	SOT-23-3	Single	SMPS	P	No	No		-20	8
AO3401	SOT-23-3	Single	General Purpose	P	No	No		-30	12
AO3401A	SOT-23-3	Single	General Purpose	P	No	No		-30	12
AO3403	SOT-23-3	Single	General Purpose	P	No	No		-30	12
AO3407	SOT-23-3	Single	General Purpose	P	No	No		-30	20
AO3407A	SOT-23-3	Single	General Purpose	P	No	No		-30	20
AO3409	SOT-23-3	Single	General Purpose	P	No	No		-30	20
AO3421	SOT-23-3	Single	General Purpose	P	No	No		-30	20
AO3421E	SOT-23-3	Single	General Purpose	P	Yes	No		-30	20
TSOP-6									
AO6400	TSOP-6	Single	General Purpose	N	No	No		30	12
AO6402	TSOP-6	Single	General Purpose	N	No	No		30	20
AO6402A	TSOP-6	Single	General Purpose	N	No	No		30	20
AO6424	TSOP-6	Single	General Purpose	N	No	No		30	20
AO6424A	TSOP-6	Single	General Purpose	N	No	No		30	20
AO6432	TSOP-6	Single	General Purpose	N	No	No		30	20
AO6404	TSOP-6	Single	Load Switch	N	No	No		20	12
AO6409	TSOP-6	Single	Load Switch	P	Yes	No		-20	8
AO6409A	TSOP-6	Single	Load Switch	P	Yes	No		-20	8
AO6415	TSOP-6	Single	Load Switch	P	Yes	No		-20	12
AO6401	TSOP-6	Single	General Purpose	P	No	No		-30	12
AO6401A	TSOP-6	Single	General Purpose	P	No	No		-30	12
AO6403	TSOP-6	Single	General Purpose	P	No	No		-30	20
AO6405	TSOP-6	Single	General Purpose	P	No	No		-30	20
AO6800	TSOP-6	Dual	General Purpose	N	No	No		30	12
AO6802	TSOP-6	Dual	General Purpose	N	No	No		30	20
AO6808	TSOP-6	Common Drain	Load Switch	N	Yes	No		20	12
AO6601	TSOP-6	Complementary	Inverter	N	No	No		30	12
AO6601	TSOP-6	Complementary	Inverter	P	No	No		-30	12
AO6602	TSOP-6	Complementary	Inverter	N	No	No		30	20
AO6602	TSOP-6	Complementary	Inverter	P	No	No		-30	20
AO6604	TSOP-6	Complementary	Inverter	N	No	No		20	8
AO6604	TSOP-6	Complementary	Inverter	P	No	No		-20	8

1. Not recommended for new designs. Please contact your local sales office for a replacement part, if any.
2. On-resistance Static Source-Source, otherwise Static Drain-Source.

I _D (A)		P _D (W)		R _{DS(ON)} (mΩ max) at V _{GS} =						VGS(th)	Ciss	Coss	Crss	Qg	Qgd	Trr	Qrr
25°C	70°C	25°C	70°C	10V	4.5V	2.5V	1.8V	1.5V	1.2V	(max V)	(pF)	(pF)	(pF)	(nC)	(nC)	(ns)	(nC)
3.6	2.9	1.4	0.9	50	70					2.5	170	35	23	2	1	7.5	2.5
3.8	3.1	1.4	0.9	55	65	85				1.5	235	35	18	4.7	1.6	8.5	2.6
3.8	3.1	1.4	0.9	55	65	85				1.5	235	35	18	4.7	1.6	8.5	2.6
4	3	1.4	0.9	52	60	78				1.5	245	35	20	2.6	1	6.5	7.5
3	2.5	1.4	0.9		62	70	85			1	260	48	27	2.9	0.6	14	3.8
6.5	5.2	1.4	0.9		22	26	34			1.1	1295	160	87	10	2.6	31	6.8
6	5	1.4	0.9	24	27	42	55			1.1	525	95	75	6	2	14	6
-3	-2.4	1.4	0.9		80	100	130			-1	560	80	70	8.5	2.1	37	27
-4	-3.5	1.5	1		41	53	65			-0.9	751	115	80	9.3	2.2	26	51
-5	-4	1.5	1		41	53	65			-0.9	751	115	80	9.3	2.2	26	51
-3.5	-2.8	1.4	0.9	85	102	140				-1.2	325	63	37	3.1	1.1	11	4.3
-2	-2	1.4	0.9	92	118	166				-1.2	325	63	37	3.2	0.9	6.1	1.4
-2.9	-2.3	1	0.6		70	90	110	130		-1	510	70	52	5.6	1.8	17	4
-4	-3.2	1.4	0.9	50	60	85				-1.3	645	80	55	7	2.5	11	3.5
-4	-3.2	1.4	0.9	50	60	85				-1.3	645	80	55	7	2.5	11	3.5
-2.6	-2.2	1.4	0.9	115	150	200				-1.4	260	37	20	2.8	1	11.5	4.5
-4.1	-3.5	1.4	0.9	52	87					2.4	520	100	65	4.6	2.2	11	5.3
-4.3	-3.5	1.4	0.9	48	78					-2.4	520	100	65	4.6	2.2	11	5.3
-2.6	-2.2	1.4	1	110	180					-2.4	197	42	26	2.2	1.1	11.3	4.4
-2.6	-2.2	1.4	1	110	180					-2.4	197	42	26	2.2	1.1	11.3	4.4
-3	-2	1.4	0.9	95	160					-2.5	215	46.5	27.5	2.2	1.2	9	16
6.9	5.8	2	1.3	28	33	52				1.45	630	75	50	6	1.8	8.5	2.6
5	4	1.25	0.8	31	43					2.4	255	45	35	2.55	1.3	8.5	2.2
7.5	6	2	1.28	24	35					2.6	373	67	41	3.5	1.7	10.5	4.5
5	4	1.25	0.8	31	43					2.4	255	45	35	2.55	1.3	8.5	2.2
6.5	5	2.5	1.5	35	48					2.4	270	50	35	3.2	1.75	10	2.3
7.5	6	2	1.28	24	35					2.6	373	67	41	3.5	1.7	10.5	4.5
8.6	6.8	2	1.28	17	18	24	33			1	1810	232	200	17.9	4.7	22	9.8
-5.5	-4.2	2.1	1.3		41	53	65			-0.9	751	115	80	9.3	2.2	26	51
-5.5	-4	2.1	1.3		41	53	65			-0.9	751	115	80	9.3	2.2	26	51
-3.3	-2.7	1.25	0.8	82	100	140				-1.2	325	63	37	3.2	0.9	6.1	1.4
-5	-4	2	1.3	47	64	85				-1.3	645	80	55	7	2.5	11	3.5
-5	-4	2	1.3	47	64	85				-1.3	645	80	55	7	2.5	11	3.5
-6	-5	2	1.3	35	58					-2.4	760	140	95	6.7	3.2	15	9.7
-5	-4.2	2	1.3	52	87					-2.4	520	100	65	4.6	2.2	11	5.3
3.4	2.7	1.15	0.73	60	70	90				1.5	235	35	18	4.7	1.6	8.5	2.55
3.5	3	1.15	0.73	50	70					2.5	170	35	23	2	1	7.5	2.5
4.6	3.7	0.8	0.5		19	23				1	620	125	64	7.7	2.7	25	9
3.4	2.7	1.15	0.73	60	70	90				1.5	235	35	18	4.7	1.6	8.5	2.55
-2.3	-1.8	1.15	0.73	115	150	200				-1.4	260	37	20	2.8	1	11.5	4.5
3.5	3	1.15	0.73	50	70					2.5	170	35	23	2	1	7.5	2.5
-2.7	-2.1	1.15	0.73	100	170					-2.4	197	42	26	2.2	1.1	11.3	4.4
3.4	2.5	1.1	0.7		65	75	100			1	260	48	27	2.9	0.6	14	3.8
-2.5	-2	1.1	0.7		75	95	115			-1	560	80	70	8.5	2.1	37	27

* For bottom exposed packages, the I_D and P_D are calculated at 100°C, otherwise at 70°C.

* R_{DS(ON)} measured at V_{GS} other than 10V, 4.5V, 1.8V, 1.5V, or 1.2V.

* Qg measured with V_{GS} = 10V. In all other cases V_{GS} = 4.5V.

Low Voltage MOSFETs (Continued)

Part Number	Package	Configuration	Popular Application	Type	ESD Diode	Schottky Diode	Schottky Type	V _{DS} (V)	V _{GS} (±V)
TSSOP-8									
AO8808A	TSSOP-8	Dual	Battery Protection	N	Yes	No		20	12
AO8801A	TSSOP-8	Dual	Load Switch	P	Yes	No		-20	8
AO8810	TSSOP-8	Common Drain	Battery Protection	N	Yes	No		20	8
AO8814	TSSOP-8	Common Drain	Battery Protection	N	Yes	No		20	12
AO8820	TSSOP-8	Common Drain	Battery Protection	N	Yes	No		20	12
AO8822	TSSOP-8	Common Drain	Battery Protection	N	Yes	No		20	12
AO8830	TSSOP-8	Common Drain	Battery Protection	N	Yes	No		20	12
DFN 1.0x0.6									
AON1606	DFN 1.6x0.6	Single	Load Switch	N	Yes	No		20	8
AON1605	DFN 1.6x0.6	Single	Load Switch	P	Yes	No		-20	8
DFN 1.6x1.6									
AON1634	DFN 1.6x1.6A	Single	Load Switch	N	Yes	No		30	12
DFN 2x2									
AON2410	DFN 2x2B	Single	Load Switch	N	No	No		30	12
AON2420	DFN 2x2B	Single	General Purpose	N	No	No		30	20
AON2408	DFN 2x2B	Single	Load Switch	N	No	No		20	12
AON2403	DFN 2x2B	Single	Load Switch	P	No	No		-12	8
AON2411	DFN 2x2C	Single	Load Switch	P	Yes	No		-12	8
AON2405	DFN 2x2B	Single	Load Switch	P	No	No		-20	8
AON2409	DFN 2x2B	Single	Load Switch	P	No	No		-30	20
AON2802	DFN 2x2	Dual	Battery Protection	N	Yes	No		30	12
AON2810	DFN 2x2	Dual	General Purpose	N	Yes	No		30	12
AON2812	DFN 2x2	Dual	General Purpose	N	Yes	No		30	12
AON2801	DFN 2x2	Dual	Load Switch	P	No	No		-20	8
AON2803	DFN 2x2	Dual	Load Switch	P	No	No		-20	8
DFN 2x5									
AON5802B	DFN 2x5	Common Drain	Battery Protection	N	Yes	No		30	12
AON5820	DFN 2x5	Common Drain	Battery Protection	N	Yes	No		20	12
DFN 3x2									
AON4420L	DFN 3x2	Single	Load Switch	N	No	No		30	20
AON4407	DFN 3x2	Single	Load Switch	P	Yes	No		-12	8
AON4703	DFN 3x2	Single	Load Switch	P	No	Yes	1 A	-20	8
AON4421	DFN 3x2	Single	Load Switch	P	No	No		-30	20
AON4803	DFN 3x2	Dual	Load Switch	P	No	No		-20	8
AON4805L	DFN 3x2	Dual	Load Switch	P	No	No		-20	8
AON4605	DFN 3x2	Complementary	Inverter	N	No	No		30	20
AON4605	DFN 3x2	Complementary	Inverter	P	No	No		-30	20
DFN 3x3									
AON3414	DFN 3x3	Single	Load Switch	N	Yes	No		30	20
AON7380	DFN 3x3	Single	SMPS	N	No	No		30	20
AON7400	DFN 3x3	Single	SMPS	N	No	No		30	12
AON7400A	DFN 3x3	Single	SMPS	N	No	No		30	20
AON7406	DFN 3x3	Single	SMPS	N	No	No		30	20
AON7408	DFN 3x3	Single	SMPS High Side	N	No	No		30	20

1. Not recommended for new designs. Please contact your local sales office for a replacement part, if any.
2. On-resistance Static Source-Source, otherwise Static Drain-Source.

I _D (A)		P _D (W)		R _{DS(ON)} (mΩ max) at V _{GS} =						VGS(th)	Ciss	Coss	Crss	Qg	Qgd	Trr	Qrr
25°C	70°C	25°C	70°C	10V	4.5V	2.5V	1.8V	1.5V	1.2V	(max V)	(pF)	(pF)	(pF)	(nC)	(nC)	(ns)	(nC)
8	6.3	1.4	1	14	15	20	28			1	1160	232	146	16	3.8	20.2	8
-4.5	-3.6	1.5	0.96		42	54	68			-0.9	751	115	80	9.3	22	26	51
7	5.7	1.5	1		20	23	28			1.1	1295	160	97	10	2.6	31	6.8
7.5	6	1.5	0.96	16	18	24	34			1	1390	190	150	15.4	4	15	5.1
7	5.5	1.5	0.96	21	24	32	50			1.1	500	100	52	6	1	9	10
7	5.7	1.5	0.96	18	22	27				1	650	140	60	6.7	3	10	11
6	4.8	1.5	0.94	27	30	41	55			1	290	120	40	5.2	1.9	25	8
0.7	0.55	0.9	0.55		275	335	390			1	62.5	12.5	9	0.85	0.25		
-0.7	-0.55	0.9	0.55		710	930	1250			-1.1	50	12	7.5	0.75	0.2		
4	3	1.8	1.15	54	62	82				1.5	245	35	20	2.6	1	6.5	7.5
8	6	2.8	1.8		21	28				1.5	813	98	56	8	2.6	10	2.4
8	6	2.8	1.8	11.7	17.5					2.2	552	227	28	4.3	1.7	13.2	3.2
8	6	2.8	1.8		14.5	19				1.2	782	158	98	7	2.4	11	2.7
-8	-6	2.8	1.8		21	28	40	54		-0.9	1370	350	258	12.7	3.4	20.7	5.2
-20	-15.5	5	3.2		8	11.6	17.5			-0.9	2180	675	425	20	5.5	28	13
-8	-6	2.8	1.8		32	41	56	70		-0.9	1025	167	119	13	3.4	15	4
-8	-6.3	2.8	1.8	32	53					-2.3	530	114	75	6	3	12.2	25.4
2	1.6	2.1	1.3	60	68	88				1.5	245	35	20	2.6	1	2	3
2	1.6	2.5	1.6	44	52	74				1.4	235	75	15	2.2	0.7	7.2	1.3
4.5	3.5	2.5	1.6	37	45	70				1.4	235	75	15	2.2	0.7	7.2	1.3
-3	-2	1.1	0.73		120	160	200			-1	540	90	63	5	1	21	9.1
-3.8	-3	1.5	0.95		70	90	115			-1	560	80	70	8.5	2.1	37	27
7.2	5.6	1.6	1		19	30				1.5	920	105	52	7.5	2.5	21.6	10
10	8	1.7	1		9.5	13				1	1255	200	168	12.5	6.5	11	15
10	8	1.6	1	19	25					2.5	550	110	55	4.6	2.2	11	13
-9	-7	2.5	1.6		20	25	31			-0.85	1740	334	200	19	5.3	22	17
-3.4	-2.7	1.7	1.1		90	120	160			-1	540	80	49	6.1	1.6	37	27
-8	-6	2.5	1.6	26	34					-1.8	930	170	120	8.6	3.4	18	32
-3.4	-2.7	1.7	1.1		90	120	165			-1	540	80	49	6.1	1.6	21	7.5
-4.5	-3.5	2	1.3		65	85	115			-1	560	80	70	8.5	2.1	37	27
4.3	3.4	1.9	1.2	65	115					3	238	35	30	3.1	1.6	7.5	2.5
-3.4	-2.7	1.9	1.2	110	180					-3	290	42	44	3	1.6	11.3	4.4
10.5	8	3.1	2	17	23					2.4	690	105	80	7.5	3	7.5	11.5
24	24*	24	9.5*	6.8	10.5					2.2	825	335	40	6.2	2.6	11	17
26	20*	35	14*	12.5	14.5					1.55	1210	330	85	10	2.7	36	47
40	28*	25	10*	7.5	10.5					2.5	1150	180	105	9.5	5	8.7	13.5
25	15*	15.5	6*	17	23					2.4	740	110	82	7.5	3	8	18
18	11.5*	11	4.5*	20	32					2.6	373	67	41	7.1	1.6	10.5	4.5

* For bottom exposed packages, the I_D and P_D are calculated at 100°C, otherwise at 70°C.

* R_{DS(ON)} measured at V_{GS} other than 10V, 4.5V, 1.8V, 1.5V, or 1.2V.

* Qg measured with V_{GS} = 10V. In all other cases V_{GS} = 4.5V.

Low Voltage MOSFETs (Continued)

Part Number	Package	Configuration	Popular Application	Type	ESD Diode	Schottky Diode	Schottky Type	V _{DS} (V)	V _{GS} (±V)
AON7410	DFN 3x3	Single	Load Switch	N	No	No		30	20
AON7414	DFN 3x3	Single	Load Switch	N	No	No		30	20
AON7422G	DFN 3x3	Single	Load Switch	N	Yes	No		30	20
AON7426	DFN 3x3	Single	Load Switch	N	Yes	No		30	20
AON7430	DFN 3x3	Single	General Purpose	N	No	No		30	20
AON7466	DFN 3x3	Single	General Purpose	N	No	No		30	25
AON7502	DFN 3x3	Single	General Purpose	N	No	No		30	25
AON7506	DFN 3x3	Single	General Purpose	N	No	No		30	20
AON7508	DFN 3x3	Single	General Purpose	N	No	No		30	20
AON7516	DFN 3x3	Single	Load Switch	N	No	No		30	20
AON7522E	DFN 3x3	Single	General Purpose	N	No	No		30	20
AON7524	DFN 3x3	Single	General Purpose	N	Yes	No		30	12
AON7530	DFN 3x3	Single	General Purpose	N	No	No		30	20
AON7532E	DFN 3x3	Single	General Purpose	N	Yes	No		30	20
AON7534	DFN 3x3	Single	General Purpose	N	No	No		30	20
AON7538	DFN 3x3	Single	General Purpose	N	No	No		30	20
AON7544	DFN 3x3	Single	General Purpose	N	No	No		30	20
AON7556	DFN 3x3	Single	General Purpose	N	No	No		30	20
AON7566	DFN 3x3	Single	General Purpose	N	Yes	No		30	20
AON7752	DFN 3x3	Single	General Purpose	N	No	Yes		30	20
AON7754	DFN 3x3	Single	General Purpose	N	No	Yes	SRFET	30	20
AON3402	DFN 3x3	Single	General Purpose	N	Yes	No		20	12
AON7404	DFN 3x3	Single	Load Switch	N	No	No		20	12
AON7407	DFN 3x3	Single	Load Switch	P	No	No		-20	8
AON3419	DFN 3x3	Single	Load Switch	P	No	No		-30	20
AON7401	DFN 3x3	Single	Load Switch	P	No	No		-30	25
AON7403	DFN 3x3	Single	Load Switch	P	No	No		-30	25
AON7409	DFN 3x3	Single	Load Switch	P	Yes	No		-30	25
AON7804	DFN 3x3	Dual	SMPS	N	Yes	No		30	20
AON7810	DFN 3x3	Dual	General Purpose	N	No	No		30	20
AON7812	DFN 3x3	Dual	General Purpose	N	No	No		30	20
AON3814	DFN 3x3	Common Drain	Battery Protection	N	Yes	No		20	12
AON3816	DFN 3x3	Common Drain	Battery Protection	N	Yes	No		20	12
AON3818	DFN 3x3	Common Drain	Battery Protection	N	Yes	No		24	12
AON3820	DFN 3x3	Common Drain	Battery Protection	N	Yes	No		24	12
AON3611	DFN 3x3	Complementary	General Purpose	N	No	No		30	20
AON3611	DFN 3x3	Complementary	General Purpose	P	No	No		-30	20
AON7611	DFN 3x3	Complementary	Inverter	N	No	No		30	20
AON7611	DFN 3x3	Complementary	Inverter	P	No	No		-30	20
AON7934	DFN 3x3	Asymmetric	SMPS	N	No	No		30	20
AON7934	DFN 3x3	Asymmetric	SMPS	P	No	No		30	20
AONR21357 <i>NEW</i>	DFN 3x3	Single	Load Switch	N	No	No		-30	25
DFN 3.3x3.3									
AON7418	DFN 3.3x3.3	Single	Load Switch	N	No	No		30	20
AON7510	DFN 3.3x3.3	Single	Load Switch	N	No	No		30	20

1. Not recommended for new designs. Please contact your local sales office for a replacement part, if any.
2. On-resistance Static Source-Source, otherwise Static Drain-Source.

I _D (A)		P _D (W)		R _{DS(ON)} (mΩ max) at V _{GS} =						VGS(th)	Ciss	Coss	Crss	Qg	Qgd	Trr	Qrr
25°C	70°C	25°C	70°C	10V	4.5V	2.5V	1.8V	1.5V	1.2V	(max V)	(pF)	(pF)	(pF)	(nC)	(nC)	(ns)	(nC)
24	15*	20	8.3*	20	26					2.5	550	110	55	4.6	2.2	9	15
20	15*	15.5	6*	15	20					2.2	595	98	70	6.8	3.6	9	15
32	32*	28	11*	4.6	7.2					2.4	2300	240	210	20	12	11	15
40	31*	29	12*	5.5	8					2.35	1756	283	155	16	6.2	12.3	25
34	21*	23	9*	12	16					2.5	760	125	70	6.6	3	7	8
30	23*	25	10*	7.5	10.5					2.5	1150	180	105	9.5	5	8.7	13.5
30	23.5*	31	12.5*	4.7	7.6*					3	1022	574	63	6.2	3.5	15.3	20
12	9.4*	20.5	8*	9.8	15.8					2.3	542	233	31	4.3	1.7	9.7	11.5
32	25*	62.5	25*	3	4.6					2.2	1835	940	90	13.6	5.3	19	36.7
30	23*	25	10*	4.5	6.8					2.2	1229	526	83	12	5.5	12.6	15.2
34	27*	31	12*	4	6.8					2.2	1540	485	448	19.7	15	15.2	22.2
28	22*	32	12.8*	3.3	4	5.8				1.2	2250	800	65	16	5.2	16	23
30	23*	24	9.6*	4.7	7.2					2.2	1320	530	70	8.8	4	13.5	20.6
28	21*	28	11*	3.5	5.5					2.2	1950	810	95	12.8	4.8	17.5	34.5
30	23*	23	9*	5	8.5					2.2	1037	441	61	6.8	3.6	12.7	17.2
30	23*	24	9*	5.1	8.2					2.2	1128	435	59	7.4	2.3	13.3	25
30	23*	23	9*	5	8.5					2.2	951	373	62	7.5	3.2	10.2	13.6
12	9.4*	12.5	5*	10.5	16.5					2.2	600	230	30	4.4	1.9	8.6	10.5
34	34*	30	12*	3.7	5.2					2.4	3020	330	280	28	17.5	12	20
16	12*	20	8.3*	8.2	14.5					2.5	605	275	36.5	5.5	2.6	11.5	12.5
32	25*	70	28*	3.6	5					2.4	1975	913	92	13.6	5.3	19	36.7
12	10	3	2	13	17	26				1	1810	232	200	17.9	4.7	20.2	8
40	31*	40	16*		6	7.5				1.6	3860	740	580	36	12	17	36
-40	-29*	29	12*		9.5	12.5	18			-0.9	3495	528	425	44*	11	33	100
-10	-7.8	3.1	2	19	32					-2.5	1040	180	125	9.6	4.5	11.5	25
-35	-23*	29	12*	14	17*					-3	2060	370	295	30*	10	14	35
-29	-18*	25	10*	18	36*					-3	1130	240	155	18*	3.3	12	26
-32	-25*	96	38.5*	8.5	17					-2.7	2142	474	363	18.5	6	17.5	44.5
22	14*	17	7*	21	26					2.4	740	110	82	7.5	3	8	18
6	5*	20.5	8*	14	20.5					2.3	542	233	31	4.3	2	8.5	9
6	4.5*	12.6	5*	14.5	20.5					2.2	600	230	30	4.4	1.9	8.6	10.5
6	5.3	2.5	1.6		17	24				1.1	920	155	75	11	3.2	7.9	4.4
4	3.1	2.5	1.6		22	28				1.1	920	155	75	11	3.2	7.9	4.4
8	6	2.7	1.7		13.5	21				1.2	840	210	205	9.5	4.5	1.7	5.2
8	6.2	2	1.3		8.9	11.8				1.3	1325	250	220	12.5*	6		
5	3.8	2.1	1.3	50	70					2.5	170	35	23	2	1	7.5	2.5
-6	-4.7	2.5	1.6	38	62					-2.4	520	100	65	4.6	2.2	11	5.3
9	5.5*	7	2.8*	50	70					2.5	170	35	23	2	1	7.5	2.5
-18.5	-11.5*	20.8	8.3	38	62					-2.4	520	100	65	4.6	2.2	11	5.3
16	12*	23	9*	10.2	15.8					2.2	485	235	32	3.9	2.1	9.9	12.9
18	14*	25	10*	7.7	11.6					2.2	807	314	40	6	3	11.3	15
-34	-32.5*	30	12	7.8	12.3					-2.3	2830	430	365	25	12	62	32
50	39*	83	33*	1.7	2.8					2.2	2994	1276	196	23	10	20	46
75	59*	46	18.5*	1.25	2.1					2.0	4500	1400	1310	60	40	23	49

* For bottom exposed packages, the I_D and P_D are calculated at 100°C, otherwise at 70°C.

* R_{DS(ON)} measured at V_{GS} other than 10V, 4.5V, 1.8V, 1.5V, or 1.2V.

* Qg measured with V_{GS} = 10V. In all other cases V_{GS} = 4.5V.

Low Voltage MOSFETs (Continued)

Part Number	Package	Configuration	Popular Application	Type	ESD Diode	Schottky Diode	Schottky Type	V _{DS} (V)	V _{GS} (±V)
AON7520	DFN 3.3x3.3	Single	Load Switch	N	Yes	No		30	12
AON7528	DFN 3.3x3.3	Single	General Purpose	N	Yes	No		30	20
AON7784	DFN 3.3x3.3	Single	SMPS Low Side	N	No	Yes		30	12
AON7421	DFN 3.3x3.3	Single	Load Switch	P	No	No		-20	12
AON7423	DFN 3.3x3.3	Single	Load Switch	P	No	No		-20	8
AON7405	DFN 3.3x3.3	Single	Load Switch	P	No	No		-30	25
DFN 5x6									
AON6204	DFN 5x6	Single	General Purpose	N	No	No		30	20
AON6312	DFN 5x6	Single	General Purpose	N	No	No		30	20
AON6314	DFN 5x6	Single	General Purpose	N	No	No		30	30
AON6354	DFN 5x6	Single	General Purpose	N	No	No		30	20
AON6358	DFN 5x6	Single	General Purpose	N	No	No		30	20
AON6360	DFN 5x6	Single	General Purpose	N	No	No		30	20
AON6362	DFN 5x6	Single	General Purpose	N	No	No		30	20
AON6366E	DFN 5x6	Single	General Purpose	N	Yes	No		30	20
AON6368	DFN 5x6	Single	General Purpose	N	No	No		30	20
AON6370	DFN 5x6	Single	General Purpose	N	No	No		30	20
AON6372	DFN 5x6	Single	General Purpose	N	No	No		30	20
AON6380	DFN 5x6	Single	General Purpose	N	No	No		30	20
AON6382	DFN 5x6	Single	General Purpose	N	No	No		30	20
AON6384	DFN 5x6	Single	General Purpose	N	No	No		30	20
AON6404A	DFN 5x6	Single	Load Switch	N	Yes	No		30	20
AON6406	DFN 5x6	Single	General Purpose	N	No	No		30	20
AON6414A	DFN 5x6	Single	SMPS High Side	N	No	No		30	20
AON6426	DFN 5x6	Single	Load Switch	N	No	No		30	20
AON6500	DFN 5x6	Single	General Purpose	N	No	No		30	20
AON6502	DFN 5x6	Single	General Purpose	N	No	No		30	20
AON6508	DFN 5x6	Single	General Purpose	N	No	No		30	20
AON6512	DFN 5x6	Single	General Purpose	N	No	No		30	20
AON6516	DFN 5x6	Single	General Purpose	N	No	No		30	20
AON6524	DFN 5x6	Single	General Purpose	N	No	No		30	20
AON6528	DFN 5x6	Single	General Purpose	N	No	No		30	20
AON6536	DFN 5x6	Single	General Purpose	N	No	No		30	20
AON6538	DFN 5x6	Single	General Purpose	N	No	No		30	20
AON6548	DFN 5x6	Single	General Purpose	N	No	No		30	20
AON6552	DFN 5x6	Single	General Purpose	N	No	No		30	20
AON6558	DFN 5x6	Single	General Purpose	N	No	No		30	20
AON6560	DFN 5x6	Single	Load Switch	N	No	No		30	20
AON6566	DFN 5x6	Single	General Purpose	N	No	No		30	20
AON6572	DFN 5x6	Single	General Purpose	N	No	No		30	12
AON6576	DFN 5x6	Single	General Purpose	N	No	No		30	20
AON6586	DFN 5x6	Single	General Purpose	N	No	No		30	20
AON6588	DFN 5x6	Single	General Purpose	N	No	No		30	20
AON6594	DFN 5x6	Single	General Purpose	N	No	No		30	20
AON6596	DFN 5x6	Single	General Purpose	N	No	No		30	20

1. Not recommended for new designs. Please contact your local sales office for a replacement part, if any.
 2. On-resistance Static Source-Source, otherwise Static Drain-Source.

I _D (A)		P _D (W)		R _{DS(ON)} (mΩ max) at V _{GS} =						VGS(th)	Ciss	Coss	Crss	Qg	Qgd	Trr	Qrr
25°C	70°C	25°C	70°C	10V	4.5V	2.5V	1.8V	1.5V	1.2V	(max V)	(pF)	(pF)	(pF)	(nC)	(nC)	(ns)	(nC)
50	39*	83.3	33.3*	1.8	2.1	3.1				1.2	4175	1505	300	37	12.5	20.3	40.7
50	39*	83	33*	2	3.4					2.2	2895	1439	149	21.3	9	22.3	54
50	39*	83	33*	3.5	4					2.1	3800	400	260	28	9	11	17
-50	-39*	83	33*	4.6	5.8	9				-1.2	4550	823	563	44	14	30	75
-50	-39*	83	33*		5	6.5	8.5	11		-0.9	5626	928	716	70	18.4	78	495
-50	-39*	83	33*	6.2	8.9*					-2.8	2450	550	370	21	12	25	47
24	19*	31	13*	12	18					2.4	510	220	22	3.5	1.4	11	17
85	83*	50	20*	1.85	2.5					2.2	3100	875	105	20	6	17	36
85	53*	32.5	13*	2.8	3.5					2.0	1900	400	60	13	3.6	12	21.5
83	52*	36	14*	3.3	5.2					2.2	1330	360	55	10	3.5	11	17
85	67*	48	19*	2.2	3.6					2.2	2200	1000	100	15	4.7	17	42
85	59*	42	17*	3	5					2.2	1590	660	80	11.5	5.8	14.5	31
60	39*	31	13*	5.2	8.6					2.2	820	340	40	6.1	2.4	11	19
34	34*	46	18*	3.7	5.2					2.4	3020	330	280	28	17	12	20
52	33*	27	11*	6.1	9.5					2.2	820	340	40	6.1	2	11	19
47	29*	26	10*	7.2	11.5					2.2	840	330	50	6.2	3.5	11	18
47	29*	26	10*	7.2	11.3					2.2	830	325	49	6.1	3.4	11	18
24	24*	26	10.5*	6.8	10.5					2.2	825	335	40	6.2	2.6	11	17
85	83*	50	20*	1.85	2.5					2.2	3100	875	105	20	6	17	36
83	52*	36	14*	3.3	5.2					2.2	1330	360	55	10	3.5	11	17
85	67*	83	33*	2.3	3					2.4	4335	720	435	33	16	29	13.5
170	110*	110	45*	2.3	3.5					2.4	4300	720	420	33	15	30	15
50	30*	31	12.5*	8	10.5					2.5	1150	180	105	9.5	5	8.7	13.5
65	43*	42	17*	5.5	7.5					2.5	1930	290	230	18	11	14	40
200	151*	83	33*	0.95	1.3					2	7036	2778	353	49.7	21.4	31	106
85	66*	83	33*	2.2	2.7					2.2	3430	1327	175	25	10.3	22	58
32	25*	41	16*	3.2	5					2.2	2010	898	124	17	8	14	20.3
150	115*	83	33*	1.7	2.4					2	3430	1327	175	25	10.3	22	58
56	25*	25	10*	5	8					2.2	1229	526	83	12	5.5	12.6	15.2
68	43*	35.5	14*	5	8.5					2.3	1080	427	92	8.1	4	12	16.8
30	23*	25	10*	6.3	9.8					2.2	1037	441	61	6.8	3.6	12.7	17.2
55	35*	35.5	14*	7	10					2.5	1210	210	100	9	3.5	9	13
75	48*	35.5	14*	4	7.4					2.4	1315	570	95	10	4.5	14	20.5
85	66*	83	33*	1.8	2.5					2.2	4290	1680	300	31.2	14.6	23.5	60
30	23*	25	10*	5	8.5					2.2	1037	441	61	6.8	3.6	12.7	17.2
30	24*	24	9.5*	5.1	8.2					2.2	1128	435	59	7.4	2.3	13.3	25
200	200*	208	83*	0.68	1.1					2.2	11500	3400	3100	130	92	38.5	120
32	25*	25	10*	5	8.5					2.4	1300	530	75	8.5	2.5	14	25
85	63.5*	48	19.2*	3.2	3.9					2	3290	855	135	20.3	4.4	16.5	31
32	25*	26	10.4*	4.7	7.2					2.2	1320	530	70	8.8	4	13.5	20.6
35	30*	41	16*	7.5	10.5					2.5	1150	180	105	9.5	5	8.7	13.5
32	25*	46	18.5*	3.3	4.8					2.2	2160	915	115	14	6.3	16.5	34.2
35	27*	39	15.5*	7	11					2.2	1037	441	61	6.8	3.6	12.7	17.2
35	30*	41	16*	7.5	10.5					2.5	1150	180	105	9.5	5	8.7	13.5

* For bottom exposed packages, the I_D and P_D are calculated at 100°C, otherwise at 70°C.

* R_{DS(ON)} measured at V_{GS} other than 10V, 4.5V, 1.8V, 1.5V, or 1.2V.

* Qg measured with V_{GS} = 10V. In all other cases V_{GS} = 4.5V.

Low Voltage MOSFETs (Continued)

Part Number	Package	Configuration	Popular Application	Type	ESD Diode	Schottky Diode	Schottky Type	V _{DS} (V)	V _{GS} (±V)
AON6661	DFN 5x6	Complementary	General Purpose	N	No	No		30	20
AON6661	DFN 5x6	Complementary	General Purpose	P	No	No		-30	20
AON6667	DFN 5x6	Complementary	General Purpose	N	No	No		30	20
AON6667	DFN 5x6	Complementary	General Purpose	P	No	No		-30	20
AON6734	DFN 5x6	Single	General Purpose	N	No	No		30	12
AON6752	DFN 5x6	Single	SMPS Low Side	N	No	Yes	SRFET	30	20
AON6756	DFN 5x6	Single	SMPS Low Side	N	No	Yes	SRFET	30	20
AON6758	DFN 5x6	Single	SMPS Low Side	N	No	Yes	SRFET	30	20
AON6764	DFN 5x6	Single	General Purpose	N	No	Yes	SRFET	30	12
AON6792	DFN 5x6	Single	General Purpose	N	No	Yes	SRFET	30	12
AON6794	DFN 5x6	Single	General Purpose	N	No	Yes	SRFET	30	12
AON6796	DFN 5x6	Single	General Purpose	N	No	Yes	SRFET	30	12
AON6522	DFN 5x6	Single	General Purpose	N	No	No		25	20
AON6403	DFN 5x6	Single	Load Switch	P	No	No		-30	20
AON6405	DFN 5x6	Single	Load Switch	P	Yes	No		-30	20
AON6407	DFN 5x6	Single	Load Switch	P	No	No		-30	25
AON6411	DFN 5x6	Single	Load Switch	P	No	No		-20	12
AON6413	DFN 5x6	Single	Load Switch	P	Yes	No		-30	25
AON6435	DFN 5x6	Single	Load Switch	P	No	No		-30	25
AON6816	DFN 5x6	Dual	General Purpose	N	Yes	No		30	20
AONS21357 <i>NEW</i>	DFN 5x6	Single	Load Switch	N	No	No		-30	25
AONS32314 <i>NEW</i>	DFN 5x6	Single	Load Switch	N	No	No		30	20
DFN 5x6 (PairFET™)									
AON6810	DFN 5x6	Common Drain	Battery Management	N	Yes	No		30	20
AON6812	DFN 5x6	Common Drain	Battery Management	N	Yes	No		30	20
AON6906A	DFN 5x6	Asymmetric	SMPS	N	No	No		30	20
AON6906A	DFN 5x6	Asymmetric	SMPS	N	No	No		30	20
AON6908A	DFN 5x6	Asymmetric	SMPS	N	No	Yes	SRFET	30	12
AON6908A	DFN 5x6	Asymmetric	SMPS	N	No	No		30	20
AON6910A	DFN 5x6	Asymmetric	SMPS	N	No	Yes	SRFET	30	12
AON6910A	DFN 5x6	Asymmetric	SMPS	N	No	No		30	20
AON6912A	DFN 5x6	Asymmetric	SMPS	N	No	No		30	20
AON6912A	DFN 5x6	Asymmetric	SMPS	N	No	No		30	20
AON6918	DFN 5x6	Asymmetric	SMPS	N	No	No		25	20
AON6918	DFN 5x6	Asymmetric	SMPS	N	No	No		25	20
AON6924	DFN 5x6	Asymmetric	SMPS	N	No	Yes	SRFET	30	12
AON6924	DFN 5x6	Asymmetric	SMPS	N	No	No		30	20
AON6926	DFN 5x6	Asymmetric	SMPS	N	No	No		30	20
AON6926	DFN 5x6	Asymmetric	SMPS	N	No	No		30	20
AON6932A	DFN 5x6	Asymmetric	SMPS	N	No	No		30	20
AON6932A	DFN 5x6	Asymmetric	SMPS	N	No	No		30	20
AON6934A	DFN 5x6	Asymmetric	SMPS	N	No	No		30	20
AON6934A	DFN 5x6	Asymmetric	SMPS	N	No	No		30	20
AON6946	DFN 5x6	Asymmetric	SMPS	N	No	No		30	20
AON6946	DFN 5x6	Asymmetric	SMPS	N	No	No		30	20

1. Not recommended for new designs. Please contact your local sales office for a replacement part, if any.
2. On-resistance Static Source-Source, otherwise Static Drain-Source.

I _D (A)		P _D (W)		R _{DS(ON)} (mΩ max) at V _{GS} =						VGS(th)	Ciss	Coss	Crss	Qg	Qgd	Trr	Qrr
25°C	70°C	25°C	70°C	10V	4.5V	2.5V	1.8V	1.5V	1.2V	(max V)	(pF)	(pF)	(pF)	(nC)	(nC)	(ns)	(nC)
16	16*	12.5	5*	14	18					2.5	760	125	70	6.6	3	7	8
-16	-12.5*	20	8*	22	35					-2.5	1040	180	125	9.6	4.6	11.5	25
16	10.5*	10	4*	25	35					2.6	373	67	41	3.5	1.6	6	6.6
-16	-12.5*	20	8*	22	35					-2.5	1040	180	125	9.6	4.6	11.5	25
85	53	32.5	13	2.8	3.5					2.0	1900	400	60	45	3.6	12	21.5
85	66*	83	33*	1.7	2.5					2.2	3509	1468	180	25.6	9.5	23	43.8
36	28*	83	33*	2.4	4					2.4	2796	1200	165	22.3	8.6	20	40
32	25*	41	16*	3.6	5					2.4	1975	913	92	13.6	5.3	19	36.7
85	60*	42	17*	2.8	3.45					1.9	2120	700	69	16.8	4.9	15.5	33
85	76*	48	19*	2	2.5					1.9	3110	930	100	21	5.6	17.5	43
85	64*	42	17*	2.8	3.5					1.9	2150	710	70	17	5	15.5	33
70	46*	31	13*	3.9	5					1.9	1350	450	60	10.5	3	13	22
200	151*	83	33*	0.95	1.3					2	7036	2778	353	49.7	21.4	31	106
-85	-67*	83	33*	3.1	4.3					-2.2	7600	1320	1050	79	33	26	78
-30	-23*	83	33*	7	8					-1.6	4580	755	564	41	17	32	77
-85	-67*	83	33*	4.5	6*					-2.6	3505	900	650	75*	23	35	75
-85	-67*	156	62.5*	2.1	2.5	3.6				-1.3	10290	1910	1395	100	36	48	178
-32	-25*	48	19*	8.5	17					-2.7	2142	474	363	18.5	6	17.5	44.5
-34	-21.5*	31	12.5*	17	34					-3	1130	240	155	10	6	13.5	29
16	16*	21	8*	6.2	9.6					2.2	1540	485	448	19.7	15	15.2	22.2
-36	-36*	48	19*	7.8	12.3					-2.3	2830	430	365	25	12	62	32
32	26*	25	10*	8.7	12.3					2.25	1420	150	95	10	4	7.5	9
20	16*	31	12.5*	4.4	6.5					2.2	1720	746	61	11	3.2	20	30
28	22*	31	12.5*	4	6					2.2	1720	746	61	11	3.2	20	30
48	30*	45	18*	11.7	17.5					2.3	570	260	20	3.5	1.4	8.6	14.1
37	23*	31	12.5*	14.4	21.3					2.4	510	220	22	3.3	1.4	9	14.7
80	62*	78	31*	3.6	4.5					2	4380	380	280	31	9	10.5	17.2
46	28*	31	12*	8.9	12.5					2.4	850	490	30	5.7	2.6	12	22
80	52*	52	20*	4.1	5					2	3415	220	232	24	10	9	14.7
37	23*	31	12.5*	14	20					2.4	510	340	22	3.3	1.4	10	15
52	33*	30	12*	7.3	10.4					2.5	1090	125	38	7	2.5	7	8
34	21*	22	9*	13.7	19.3					2.5	760	490	70	6.6	3	13	25
60	38*	31	12.5*	5.2	7.8					2.3	1300	530	35	7.2	1.8	21	39
85	66*	104	41.5*	1.8	2.7					2.3	4000	1680	65	23	6	23	75
85	66*	104	14.5*	1.6	1.9					2.1	8190	900	670	60	20	16	34
60	38*	31	12.5*	5.2	7.8					2.3	1300	530	35	7.2	1.8	21	39
50	32*	35	14*	8.5	12					2.4	1130	180	40	8	3	8.7	13.5
44	28*	31	12.5*	11	14					2.5	1150	465	105	9.5	5	12	23
28	22*	31	12*	5	8.5					2.2	1037	441	61	6.8	3.6	12.7	17.2
42	33*	78	31*	2.5	3.2					1.9	3430	1327	175	25	10.3	22	58
28	22*	31	12*	5.2	9.5					2.2	1037	441	61	6.8	3.6	12	17.2
36	28*	33	13*	2.9	4.4					2.2	2010	898	124	17	8	14	20.3
16	12*	7.3	2.9*	11.6	17					2.2	485	235	32	3.9	2.1	9.9	12.9
18	14*	13	5.2*	7.8	11.8					2.2	807	314	40	6	3	11.3	15

* For bottom exposed packages, the I_D and P_D are calculated at 100°C, otherwise at 70°C.

* R_{DS(ON)} measured at V_{GS} other than 10V, 4.5V, 1.8V, 1.5V, or 1.2V.

* Qg measured with V_{GS} = 10V. In all other cases V_{GS} = 4.5V.

Low Voltage MOSFETs (Continued)

Part Number	Package	Configuration	Popular Application	Type	ESD Diode	Schottky Diode	Schottky Type	V _{DS} (V)	V _{GS} (±V)
AON6974A	DFN 5x6	Asymmetric	SMPS	N	No	No		30	20
AON6974A	DFN 5x6	Asymmetric	SMPS	N	No	No		30	20
AON6978	DFN 5x6	Asymmetric	SMPS	N	No	No		30	20
AON6978	DFN 5x6	Asymmetric	SMPS	N	No	Yes	SRFET	30	12
AON6980	DFN 5x6	Asymmetric	SMPS	N	No	No		30	20
AON6980	DFN 5x6	Asymmetric	SMPS	N	No	Yes	SRFET	30	12
AON6992	DFN 5x6	Asymmetric	SMPS	N	No	No		30	20
AON6992	DFN 5x6	Asymmetric	SMPS	N	No	Yes	SRFET	30	12
AON6994	DFN 5x6	Asymmetric	SMPS	N	No	No		30	20
AON6994	DFN 5x6	Asymmetric	SMPS	N	No	Yes	SRFET	30	12
AON6996	DFN 5x6	Asymmetric	SMPS	N	No	No		30	20
AON6996	DFN 5x6	Asymmetric	SMPS	N	No	Yes	SRFET	30	12
AON6998	DFN 5x6	Asymmetric	SMPS	N	No	No		30	20
AON6998	DFN 5x6	Asymmetric	SMPS	N	No	Yes	SRFET	30	12
DFN 5x6E (XSPairFET™)									
AOE6930	DFN 5x6E	Asymmetric	General Purpose	N	No	No		30	20
AOE6930	DFN 5x6E	Asymmetric	General Purpose	N	No	No		30	12
AOE6932	DFN 5x6E	Asymmetric	General Purpose	N	No	No		30	20
AOE6932	DFN 5x6E	Asymmetric	General Purpose	N	No	No		30	12
AOE6936	DFN 5x6E	Asymmetric	General Purpose	N	No	No		30	20
AOE6936	DFN 5x6E	Asymmetric	General Purpose	N	No	No		30	20
SO-8									
AO4310	SO-8	Single	General Purpose	N	No	No		36	20
AO4306	SO-8	Single	General Purpose	N	No	No		30	20
AO4354	SO-8	Single	General Purpose	N	No	No		30	20
AO4404B	SO-8	Single	General Purpose	N	No	No		30	12
AO4406A	SO-8	Single	General Purpose	N	No	No		30	20
AO4430	SO-8	Single	General Purpose	N	No	No		30	20
AO4446	SO-8	Single	SMPS High Side	N	No	No		30	20
AO4466	SO-8	Single	SMPS High Side	N	No	No		30	20
AO4468	SO-8	Single	Load Switch	N	No	No		30	20
AO4476A	SO-8	Single	SMPS	N	No	No		30	20
AO4490	SO-8	Single	Load Switch	N	Yes	No		30	20
AO4492	SO-8	Single	SMPS High Side	N	No	No		30	20
AO4494	SO-8	Single	SMPS High Side	N	No	No		30	20
AO4496	SO-8	Single	SMPS	N	No	No		30	20
AO4498	SO-8	Single	Load Switch	N	No	No		30	20
AO4568	SO-8	Single	General Purpose	N	No	No		30	20
AO4576	SO-8	Single	General Purpose	N	No	No		30	20
AO4752	SO-8	Single	General Purpose	N	No	Yes	SRFET	30	20
AO4402	SO-8	Single	Load Switch	N	No	No		20	12
AO4453	SO-8	Single	Load Switch	P	No	No		-12	8
AO4335	SO-8	Single	Load Switch	P	No	No		-30	25
AO4403	SO-8	Single	General Purpose	P	No	No		-30	12

1. Not recommended for new designs. Please contact your local sales office for a replacement part, if any.
2. On-resistance Static Source-Source, otherwise Static Drain-Source.

I _D (A)		P _D (W)		R _{DS(ON)} (mΩ max) at V _{GS} =						VGS(th)	Ciss	Coss	Crss	Qg	Qgd	Trr	Qrr
25°C	70°C	25°C	70°C	10V	4.5V	2.5V	1.8V	1.5V	1.2V	(max V)	(pF)	(pF)	(pF)	(nC)	(nC)	(ns)	(nC)
28	22*	31	12	5.2	9.5					2.2	1037	441	61	6.8	3.6	12.7	17.2
32	25*	33	13*	3.3	5					2.2	1975	913	92	13.6	5.3	19	36.7
28	22*	31	12*	5.7	9.4					2.2	1010	474	50	6.8	2.5	14	24
36	28*	33	13*	3.8	4.9					2	3276	513	57	20.6	4.6	13.6	24.7
28	22*	23.5	9.4*	6.8	10.3					2.2	1095	270	28	6.4	2	11	24
36	28*	32	13*	3.8	4.9					2	3440	515	60	21	3.7	15.7	31.8
50	31*	21	8*	5.2	8.6					2.2	820	340	40	6.1	2.4	11	19
85	67*	45	18*	2	2.5					1.9	3110	930	100	21	5.6	17.5	43
50	31*	21	8*	5.2	8.6					2.2	820	340	40	6.1	2.4	11	19
82	54*	31	13*	2.8	3.5					1.9	2150	710	70	17	5	15.5	33
50	31*	21	8.3*	5.2	8.6					2.2	820	340	40	6.1	2.4	11	19
60	38*	22	8.6*	3.9	5					1.9	1350	450	60	10.5	3	13	22
50	31*	21	8*	5.2	8.6					2.2	820	340	40	6.1	2.4	11	19
82	54*	31	13*	2.6	2.99					1.9	2150	710	70	17	5	15.5	33
22	22*	24	9.6*	4.3	7					2.1	1075	480	55	7	2.5	12.5	21.5
85	85*	75	30*	0.83	1.05					1.9	5560	1670	200	42	12	23	72.5
55	35*	24	9.6*	5	8					2.2	1150	380	55	7.5	3	11.5	20
85	85*	52	20*	1.4	1.8					1.9	4180	880	125	30	7	17	42
55	35*	24	9.6*	5	8					2.2	1150	380	55	7.5	3	11.5	20
85	67*	39	15*	2	3					2.1	2270	650	90	15	4.5	14.5	30
27	22	3.6	2.3	3.1	4.2					2.3	3248	1130	54	20.6	6.2	21.7	60.5
13	10.4	3.1	2	11.5	15.5					2.5	760	125	70	6.6	3	7	8
23	14	3.1	1.2	3.7	5.3					2.2	2010	898	124	17	8	14	20.3
8.5	7.1	3.1	2	24	30	48				1.45	630	75	50	6	1.8	8.5	2.6
13	10.4	3.1	2	11.5	15.5					2.5	760	125	70	6.6	3	7	8
18	15	3	2.1	5.5	7.5					2.5	6060	638	355	48	15	33.5	22
15	12	3	2.1	8.5	14.5					3	1520	306	214	17	10	24	19
10	7	3.1	2	23	35					2.6	373	67	41	3.5	1.6	6	6.6
10.5	8.5	3.1	2	17	23					2.4	740	110	82	7.5	3	18	9
15	12	3.1	2	7.7	10.8					2.5	1150	180	105	9.5	5	8.7	13.5
16	13	2.8	1.8	7.2	10					2.5	1803	387	238	19	8.7	27	17
14	11.4	3.1	2	9.5	14					2.2	770	240	77	7.1	3.1	11	23
18	14	3.1	2	6.5	9.5					2.5	1590	240	145	15	7.8	28	24
10	7.5	3.1	2	19.5	26					2.5	550	110	55	4.6	2.2	22	14
18	14	3.1	2	5.5	7.5					2.5	1910	316	227	18	11	14	40
12	9.4	2.5	1.6	11.5	17.5					2.2	600	230	30	4.4	1.9	8.6	10.5
20	12	3.1	1.2	5.8	9.8					2.2	1037	441	61	6.8	3.6	12.7	17.2
15	12	3.1	2	8.8	15.5					2.5	605	275	36.5	5.5	2.6	11.5	12.5
20	16	3.1	2		5.5	7				1.6	3860	740	580	36	12	17	36
-9	-7	2.5	1.6		19	26	36	50		-0.9	1370	350	258	12.7	3.4	20.7	5.2
-10.5	-8	3.1	2	18	36*					-3	1130	240	155	9.5	3.3	25	12
-6	-5	3.1	2	48	57	80				-1.3	645	80	55	7	2.5	11	3.5

* For bottom exposed packages, the I_D and P_D are calculated at 100°C, otherwise at 70°C.
 * R_{DS(ON)} measured at V_{GS} other than 10V, 4.5V, 1.8V, 1.5V, or 1.2V.
 * Qg measured with V_{GS} = 10V. In all other cases V_{GS} = 4.5V.

Low Voltage MOSFETs (Continued)

Part Number	Package	Configuration	Popular Application	Type	ESD Diode	Schottky Diode	Schottky Type	V _{DS} (V)	V _{GS} (±V)
AO4405	SO-8	Single	General Purpose	P	No	No		-30	20
AO4405E	SO-8	Single	General Purpose	P	Yes	No		-30	20
AO4407	SO-8	Single	Load Switch	P	No	No		-30	25
AO4407A	SO-8	Single	Load Switch	P	No	No		-30	25
AO4409	SO-8	Single	Load Switch	P	No	No		-30	20
AO4411	SO-8	Single	General Purpose	P	No	No		-30	20
AO4413	SO-8	Single	Load Switch	P	No	No		-30	25
AO4419	SO-8	Single	General Purpose	P	No	No		-30	20
AO4423	SO-8	Single	Load Switch	P	Yes	No		-30	25
AO4435	SO-8	Single	Load Switch	P	No	No		-30	25
AO4447A	SO-8	Single	Load Switch	P	Yes	No		-30	20
AO4449	SO-8	Single	Load Switch	P	No	No		-30	20
AO4455	SO-8	Single	Load Switch	P	Yes	No		-30	25
AO4459	SO-8	Single	Load Switch	P	No	No		-30	20
AO4425	SO-8	Single	Load Switch	P	Yes	No		-38	25
AO4840E	SO-8	Dual	General Purpose	N	No	No		40	20
AO4800B	SO-8	Dual	General Purpose	N	No	No		30	12
AO4812	SO-8	Dual	General Purpose	N	No	No		30	20
AO4818B	SO-8	Dual	General Purpose	N	Yes	No		30	20
AO4822	SO-8	Dual	General Purpose	N	No	No		30	20
AO4822A	SO-8	Dual	General Purpose	N	No	No		30	20
AO4832	SO-8	Dual	SMPS	N	No	No		30	20
AO4838	SO-8	Dual	SMPS	N	No	No		30	20
AO4842	SO-8	Dual	General Purpose	N	No	No		30	20
AO4854	SO-8	Dual	SMPS	N	Yes	No		30	20
AO4862	SO-8	Dual	Inverter	N	No	No		30	20
AO4862E	SO-8	Dual	Inverter	N	Yes	No		30	20
AO4806	SO-8	Dual	General Purpose	N	Yes	No		20	12
AO9926B	SO-8	Dual	Battery Protection	N	No	No		20	12
AO9926C	SO-8	Dual	Battery Protection	N	No	No		20	12
AO4801A	SO-8	Dual	General Purpose	P	No	No		-30	12
AO4803A	SO-8	Dual	General Purpose	P	No	No		-30	20
AO4805	SO-8	Dual	Load Switch	P	No	No		-30	25
AO4807	SO-8	Dual	General Purpose	P	No	No		-30	20
AO4813	SO-8	Dual	General Purpose	P	No	No		-30	20
AO4815	SO-8	Dual	Load Switch	P	Yes	No		-30	25
AO4606	SO-8	Complementary	Inverter	N	No	No		30	20
AO4606	SO-8	Complementary	Inverter	P	No	No		-30	20
AO4616	SO-8	Complementary	Inverter	N	No	No		30	20
AO4616	SO-8	Complementary	Inverter	P	No	No		-30	20
AO4620	SO-8	Complementary	Inverter	N	No	No		30	20
AO4620	SO-8	Complementary	Inverter	P	No	No		-30	20
AO4627	SO-8	Complementary	Inverter	N	No	No		30	20
AO4627	SO-8	Complementary	Inverter	P	No	No		-30	20

1. Not recommended for new designs. Please contact your local sales office for a replacement part, if any.
2. On-resistance Static Source-Source, otherwise Static Drain-Source.

I _D (A)		P _D (W)		R _{DS(ON)} (mΩ max) at V _{GS} =						VGS(th)	Ciss	Coss	Crss	Qg	Qgd	Trr	Qrr
25°C	70°C	25°C	70°C	10V	4.5V	2.5V	1.8V	1.5V	1.2V	(max V)	(pF)	(pF)	(pF)	(nC)	(nC)	(ns)	(nC)
-6	-5.1	3.1	2	50	85					-2.4	520	100	65	4.6	2.2	11	5.3
-6	-4.7	2.5	1.6	45	80					-1.5	495	100	56	4.2	2	9	13.5
-12	-10	3.1	2	14	30*					-2.8	2060	370	295	30*	10	30	22
-12	-10	3.1	2	13	17*					-3	2060	370	295	30*	10	30	22
-15	-12.8	3.1	2	7.5	12					-2.7	5270	945	745	51.5	23	36.7	28
-8	-6.6	3.1	2	32	55					-2.4	760	140	95	6.7	3.2	15	9.7
-15	-12.8	3.1	2	8.5						-3.5	2890	585	470	51*	16	18	11
-9.7	-7.8	3.1	2	20	35					-2.5	1040	180	125	9.6	4.6	11.5	25
-17	-14	3.1	2	7.2						-2.6	2527	583	397	47*	14	26.1	12.3
-10.5	-8	3.1	2	18	36					-3	1130	240	155	9.5	3.3	25	12
-17	-13	3.1	2	7	8					-1.6	4580	755	564	41	17	32	77
-7	-5.5	3.1	2	34	54					-2.4	760	140	95	6.7	3.2	15	9.7
-17	-14	3.1	2	7.2						-2.6	2823	574	424	54*	16	22.3	8.8
-6.5	-5.3	3.1	2	46	72					-2.4	520	100	65	4.6	2.2	11	5.3
-14	-11	3.1	2	11						-3.5	3800	560	350	63*	16.1	35	33
6	5	2	1.2	28	35					2.6	520	65	32	4.5	16.2	8	13
6.9	5.8	2	1.3	27	32	50				1.5	630	75	50	6	1.8	8.5	2.6
6	5	2	1.3	30	42					2.4	255	45	35	2.55	1.3	8.5	2.2
8.5	6.5	2	1.3	19	26					2.4	740	110	82	7.5	3	8	18
8	6.5	2	1.3	19	26					2.4	740	110	82	7.5	3	8	18
8.5	6.5	2	1.3	19	26					2.4	740	110	82	7.5	3	8	18
10	8	2	1.3	13	17.5					2.5	760	125	70	6.6	3	7	8
11	9	2	1.3	9.6	13					2.6	1080	180	110	8	3	8.5	13
7.7	6.5	2	1.44	21	30					2.6	373	67	41	3.5	1.7	10.5	4.5
8	6.5	2	1.3	19	23					2.4	740	110	82	7.5	3	8	18
4.5	3.5	1.7	1.1	50	68					2.5	200	35	25	2	1	7.5	2.5
4.5	3.5	1.7	1.1	46	65					2.5	215	35	20	2	1	5.5	7
9.4	7.5	2	1.28	14	16	22	30			1	1810	232	200	17.9	4.7	22	8.6
7.6	6.1	2	1.28	23	26	34	52			1.1	525	95	75	6	2	14	6
7.6	6.1	2	1.28	23	26	34	52			1.1	525	95	75	6	2	14	6
-5	-4	2	1.3	48	57	80				-1.3	645	80	55	7	2.5	11	3.5
-5	-4	2	1.3	46	74					-2.5	520	100	65	4.6	2.2	11	5.3
-9	-7	2	1.3	18						-2.8	2060	370	295	30*	10	30	22
-6	-5	2	1.3	35	58					-2.4	760	140	95	6.7	3.2	15	9.7
-7.1	-5.6	2	1.3	25	40					-2.5	1040	180	125	9.3	4.6	11.5	25
-8	-6.9	2	1.44	20						-3	2330	480	320	41*	12	28	20.5
6	5	2	1.3	30	42					2.4	255	45	35	2.55	1.3	8.5	2.2
-6.5	-5.3	2	1.3	28	44					-2.4	760	140	95	6.7	3.2	15	9.7
8.5	6.5	2	1.3	20	28					2.4	740	110	82	7.5	3	8	18
-7	-6	2	1.3	22	40					-2.5	1040	180	125	9.6	4.6	11.5	25
7.2	6.2	2	1.44	24	36					2.6	373	67	41	3.5	1.7	10.5	4.5
-5.3	-4.5	2	1.44	32	55					-2.4	760	140	95	6.7	3.2	15	9.7
4.5	3.5	2	1.3	50	68					2.5	170	35	23	2	1	7.5	2.5
-3.5	-2.5	2	1.3	100	165					-2.4	197	42	26	2.2	1.1	11.3	4.4

* For bottom exposed packages, the I_D and P_D are calculated at 100°C, otherwise at 70°C.

* R_{DS(ON)} measured at V_{GS} other than 10V, 4.5V, 1.8V, 1.5V, or 1.2V.

* Qg measured with V_{GS} = 10V. In all other cases V_{GS} = 4.5V.

Low Voltage MOSFETs (Continued)

Part Number	Package	Configuration	Popular Application	Type	ESD Diode	Schottky Diode	Schottky Type	V _{DS} (V)	V _{GS} (±V)
AO4629	SO-8	Complementary	Inverter	N	No	No		30	20
AO4629	SO-8	Complementary	Inverter	P	No	No		-30	20
AO4630	SO-8	Complementary	Inverter	N	No	No		30	12
AO4630	SO-8	Complementary	Inverter	P	No	No		-30	12
AO4914	SO-8	Asymmetric	SMPS	N	No	No		30	20
AO4914	SO-8	Asymmetric	SMPS	N	No	Yes	1A	30	20
AO4924	SO-8	Asymmetric	SMPS	N	No	No		30	12
AO4924	SO-8	Asymmetric	SMPS	N	No	Yes	SRFET	30	12
AO4948	SO-8	Asymmetric	SMPS	N	No	No		30	20
AO4948	SO-8	Asymmetric	SMPS	N	No	Yes	SRFET	30	20
AO4952	SO-8	Asymmetric	SMPS	N	No	No		30	20
AO4952	SO-8	Asymmetric	SMPS	N	No	Yes	SRFET	30	20
AOSP21357 <i>NEW</i>	SO-8	Single	Load Switch	N	Yes	No		-30	25
AOSP32368 <i>NEW</i>	SO-8	Single	Load Switch	N	Yes	No		30	20
Ultra SO-8									
AOL1202	Ultra SO-8	Single	SMPS	N	No	No		30	20
AOL1208	Ultra SO-8	Single	SMPS	N	No	No		30	20
AOL1432	Ultra SO-8	Single	SMPS High Side	N	No	No		25	20
AOL1404	Ultra SO-8	Single	Load Switch	N	No	No		20	12
TO-251A									
AOI418	TO-251A	Single	SMPS High Side	N	No	No		30	20
AOI514	TO-251A	Single	General Purpose	N	No	No		30	20
AOI530	TO-251A	Single	General Purpose	N	No	No		30	20
AOI538	TO-251A	Single	General Purpose	N	No	No		30	20
AOI403	TO-251A	Single	Load Switch	P	No	No		-30	25
AOI423	TO-251A	Single	General Purpose	P	No	No		-30	25
TO-251B									
AOY526	TO-251B	Single	General Purpose	N	No	No		30	20
TO-252									
AOD418	TO-252	Single	SMPS High Side	N	No	No		30	20
AOD480	TO-252	Single	General Purpose	N	No	No		30	20
AOD508	TO-252	Single	General Purpose	N	No	No		30	20
AOD522P	TO-252	Single	General Purpose	N	No	No		30	20
AOD528	TO-252	Single	General Purpose	N	No	No		30	20
AOD536	TO-252	Single	General Purpose	N	No	No		30	20
AOD538	TO-252	Single	General Purpose	N	No	No		30	20
AOD558	TO-252	Single	General Purpose	N	No	No		30	20
AOD4132	TO-252	Single	SMPS Low Side	N	No	No		30	20
AOD424	TO-252	Single	General Purpose	N	No	No		20	12
AOD403	TO-252	Single	Load Switch	P	No	No		-30	25
AOD417	TO-252	Single	Inverter	P	No	No		-30	20
AOD423	TO-252	Single	General Purpose	P	No	No		-30	25
AOD607A	TO-252	Complementary	Inverter	N	No	No		30	20
AOD607A	TO-252	Complementary	Inverter	P	No	No		-30	20
AOD661	TO-252	Complementary	Inverter	P	No	No		-30	20

1. Not recommended for new designs. Please contact your local sales office for a replacement part, if any.
2. On-resistance Static Source-Source, otherwise Static Drain-Source.

I _D (A)		P _D (W)		R _{DS(ON)} (mΩ max) at V _{GS} =						VGS(th)	Ciss	Coss	Crss	Qg	Qgd	Trr	Qrr
25°C	70°C	25°C	70°C	10V	4.5V	2.5V	1.8V	1.5V	1.2V	(max V)	(pF)	(pF)	(pF)	(nC)	(nC)	(ns)	(nC)
6	5	2	1.3	30	42					2.4	250	45	35	2.55	1.3	8.5	2.2
-5.5	-4.5	2	1.3	41	74					-2.5	520	100	65	4.6	2.2	11	5.3
7	5.6	2	1.3	23	28	36				1.45	670	75	45	6	14.5	6.5	7.5
-5	-4	2	1.3	48	57	78				-1.3	700	80	60	7		15	40
8.5	6.5	2	1.3	20.5	28					2.4	730	165	82	7.5	3	8	8
8.5	6.5	2	1.3	20.5	28					2.4	740	110	82	7.5	3	8	18
7.3	5.9	2	1.3	24	29					1.5	900	224	65	10	3.75	10	6.8
9	7.2	2	1.3	15.8	19.5					2.4	1450	88	92	12	4.2	16.8	8
8	6.5	2	1.3	19	28					2.4	740	308	82	7.5	3	11.2	10.5
8.8	7.1	2	1.3	16	22					2.2	1267	110	118	10.4	3.6	8	18
11	9	2	1.3	11.5	16.5					2.2	542	233	31	4.3	1.7	11	12.5
11	9	2	1.3	10.5	15.5					2.5	605	275	37	4.9	2.3	9.7	11.5
-16	-12.5	3.1	2	8.5	13					-2.3	2830	430	365	25	12	62	32
16	12	3.1	2	5.5	7.5					2.4	2270	245	200	18	10	10.5	16
54	42*	58	29*	4.2	6					2.3	1840	720	63	12	4.2	15	2
50	36*	50	25*	11	15					2.4	850	380	30	7	3.5	12	23
44	31*	30	15*	8.5	14					3	1430	319	215	13.5	7.75	23.06	15.25
45	35*	60	30*		4	5.6				1.6	3860	740	580	36	12	17	36
36	28*	50	25*	8	11.5					2.5	1150	180	105	9.5	5	8.7	13.5
46	36*	50	25*	5.9	11.9					2.4	1187	483	60	8.8	3.6	14.7	24
70	55*	83	41*	2.7	4.2					2.2	3130	1330	225	21.5	9.6	23	55
70	54*	93	46*	3.1	4.8					3.1	2160	915	115	14	6.3	16.5	34.2
-70	-55*	90	45*	8.5						-3.5	2890	585	470	51*	16	18	11
-70	-67*	90	45*	8.5						-3.5	2760	550	375	45*	12	15	30
50	39*	50	25*	5	9					2.4	1300	530	75	8.5	2.5	14	25
36	28*	50	25*	7.5	11					2.5	1150	180	105	9.5	5	8.7	13.5
25	18*	21	11*	23	33					2.6	373	67	41	3.5	1.6	10.5	4.5
70	55*	50	25*	3	4.5					2.2	2010	898	124	17	8	14	20.3
46	36*	53	26*	5.2	9.5					2.4	1150	500	60	8.8	23.3	14.7	24
50	39*	50	25*	5.4	9.5					2.4	1187	483	60	8.8	3.6	14.7	24
46	36*	37.5	18.5*	8.5	14.7					2.2	1140	400	45	6.5	2.5	12	20
70	54*	93	46*	3.1	4.8					3.1	2160	915	115	14	6.3	16.5	34.2
50	39*	50	25*	5.4	9.5					2.4	1187	483	60	4.1	3.6	14.7	24
85	63*	100	50*	4	6					3	3700	700	390	33	17.6	34	30
45	35*	100	50*	4.4	5.7					1.6	3860	740	580	36	12	17	36
-70	-55*	90	45*	8						-3.5	2890	585	470	51*	16	18	11
-25	-20*	50	25*	34	55					-3	920	140	90	8.2	3.6	23	14
-70	-67*	90	45*	8						-3.5	2760	550	375	45*	12	15	30
8	8*	19	7.5*	25	38					2.6	395	67	41	3.5	1.7	6	6.6
-12	-9.4*	30	12*	27	45					-2.4	730	140	90	6.7	3.2	12	25.5
-12	-9.4*	31	12.5*	22.5	36					-2.5	1040	180	125	9.6	4.6	11.5	25

* For bottom exposed packages, the I_D and P_D are calculated at 100°C, otherwise at 70°C.

* R_{DS(ON)} measured at V_{GS} other than 10V, 4.5V, 1.8V, 1.5V, or 1.2V.

* Qg measured with V_{GS} = 10V. In all other cases V_{GS} = 4.5V.

Medium Voltage MOSFETs

Part Number	Package	Configuration	Popular Application	Type	ESD Diode	Schottky Diode	Schottky Type	V _{DS} (V)	V _{GS} (±V)
SOT-223									
AOH3254	SOT-223	Single	General Purpose	N	No	No		150	20
AOH3106	SOT-223	Single	General Purpose	N	No	No		100	20
SOT-23									
AO3442	SOT-23-3	Single	General Purpose	N	No	No		100	20
AO3422	SOT-23-3	Single	General Purpose	N	No	No		55	12
TSOP-6									
AO6420	TSOP-6	Single	General Purpose	N	No	No		60	20
DFN 2x2									
AON2392	NEW	DFN 2x2C	Single	General Purpose	N	No	No	100	20
AON2290		DFN 2x2B	Single	Load Switch	N	No	No	100	20
AON2260		DFN 2x2B	Single	General Purpose	N	No	No	60	20
AON2240		DFN 2x2B	Single	General Purpose	N	No	No	40	20
DFN 3x3									
AON7460	DFN 3x3	Single	General Purpose	N	No	No		300	30
AON7462	DFN 3x3	Single	General Purpose	N	No	No		300	30
AON7458	DFN 3x3	Single	General Purpose	N	No	No		250	30
AON7296	DFN 3x3	Single	General Purpose	N	No	No		100	20
AON7262E	DFN 3x3	Single	General Purpose	N	Yes	No		60	20
AON7264E	DFN 3x3	Single	General Purpose	N	Yes	No		60	20
AON7446	DFN 3x3	Single	General Purpose	N	No	No		60	20
AON7240	DFN 3x3	Single	SMPS	N	No	No		40	20
DFN 3.3x3.3									
AON7254	DFN 3.3x3.3	Single	SMPS	N	No	No		150	20
AON7230	DFN 3.3x3.3	Single	SMPS	N	No	No		100	20
AON7232	DFN 3.3x3.3	Single	SMPS	N	No	No		100	20
AON7290	DFN 3.3x3.3	Single	SMPS	N	No	No		100	20
AON7292	DFN 3.3x3.3	Single	SMPS	N	No	No		100	20
AON7280	DFN 3.3x3.3	Single	SMPS	N	No	No		80	20
AON7140	DFN 3.3x3.3	Single	SMPS	N	No	No		40	20
AON7242	DFN 3.3x3.3	Single	SMPS	N	No	No		40	20
DFN 5x6									
AON6458	DFN 5x6	Single	General Purpose	N	No	No		250	30
AON6250	DFN 5x6	Single	General Purpose	N	No	No		150	20
AON6220	DFN 5x6	Single	SMPS	N	No	No		100	20
AON6224A	NEW	DFN 5x6	Single	SMPS	N	No	No	100	20
AON6226	DFN 5x6	Single	SMPS	N	No	No		100	20
AON6290	DFN 5x6	Single	SMPS	N	No	No		100	20
AON6292	DFN 5x6	Single	SMPS	N	No	No		100	20
AON6294	DFN 5x6	Single	SMPS	N	No	No		100	20
AON6298	DFN 5x6	Single	SMPS	N	No	No		100	20
AON6452	DFN 5x6	Single	SMPS	N	No	No		100	25
AON6482	DFN 5x6	Single	General Purpose	N	No	No		100	20
AON6484	DFN 5x6	Single	General Purpose	N	No	No		100	20
AON6850	DFN 5x6	Single	General Purpose	N	No	No		100	25

1. Not recommended for new designs. Please contact your local sales office for a replacement part, if any.
2. On-resistance Static Source-Source, otherwise Static Drain-Source.

I _D (A)		P _D (W)		R _{DS(ON)} (mΩ max) at V _{GS} =						V _{GS(th)}	C _{iss}	C _{oss}	C _{rss}	Q _g	Q _{gd}	T _{rr}	Q _{rr}
25°C	70°C	25°C	70°C	10V	4.5V	2.5V	1.8V	1.5V	1.2V	(max V)	(pF)	(pF)	(pF)	(nC)	(nC)	(ns)	(nC)
5	4	4.1	2.6	63	77					2.7	675	78	4	5.5	2.5	37	210
2	1.5	3.1	2	360	385					2	185	19	8	2.5	1.4	17	14.5
1	0.8	1.4	0.9	630	720					2.9	100	13	5	1.5	0.8	52	60
2.1	1.7	1.25	0.8		160	200				2	214	31	12.6	2.6	0.8	20	17
4.2	3.4	2	1.28	60	75					3	450	60	25	4.3	2.2	25.1	28.7
8	6*	4.1	2.6	32	39					2.4	840	64	4	6.1	1.8	20	70
4.5	3.5*	2.8	1.8	72	97					2.8	415	32	3	3	1.5	16	44
6	4.7	2.8	1.8	44	53					2.5	426	50	5	2.6	0.8	27	12
8	6*	2.8	1.8	21	29					2.4	415	112	11	3	1.1	12.5	3.5
4	2.5*	33	13*	830						4.5	310	45	2.9	6.8	2	88	290
2.5	1.6*	25	10*	1500						4.5	197	30	2	4.6*	1.5	95	220
5	3.2*	33	13*	560						4.3	306	51	3.2	6	1.5	77	290
12.5	8*	20.8	8.3*	66	90					2.8	415	32	3	3	1.5	16	44
34	34*	43	17	6.2	8.5					2.2	1652	520	52	15	6.5	19	60
28	28*	27.5	11*	9.5	13.3					2.4	1100	300	28	7	3.5	19	65
8	5*	16.7	7*	145	160*					3.3	237	25	9	4.4*	1.1	7.7	13
40	31*	36.7	14*	5.1	7					2.4	1830	521	43	12.8	6	16.5	40
17	11*	39	15.5*	54	66					2.7	675	78	4	5.5	2.5	37	210
47	30*	54	21*	11.5	15.5					2.5	2320	175	11	13	3	25	120
37	23*	39	15.5*	13.5	16.5					2.5	1770	145	10	12	4.5	23	96
50	35*	83	33*	12.6	18*					3.4	2075	175	9.5	9	4	35	185
23	15*	28	11*	24	32					2.6	1170	90	8	8	3.5	24	110
50	39*	83	33*	8.5	12*					3.4	1871	265	14	26.5*	4	32	162
50	50*	46	18.5*	2.3	3.5					2.4	3350	580	65	18	21.2	16	42
50	39*	83	33*	3.9	5.8					2.3	1970	540	41	11.9	2.2	16	47
14	8.8*	83	33*	170						4.5	1028	167	11	22*	8	158	1000
52	32*	104	41.5*	16.5	19*					3.4	2388	213	9.5	30.5*	4.5	68	560
48	48*	113.5	45.5*	6.2	7.4					2.3	4525	345	22.5	30	9	32	162
34	31*	56.5	22.5*	11.6	15.1					2.5	2305	180	11.5	15.5	5	29.5	160
48	48*	108	43*	7.9	10.2					2.3	3130	245	12.5	18.5	4.5	30	150
85	67*	208	83*	4.6	6.2*					3.4	4600	415	27	28.5	10	40	230
85	67*	156	62.5*	6	8.5*					3.4	3830	327	16.5	15.5	7	19	225
52	33*	57	23*	10	14*					3.5	2265	195	10	28*	4	35	195
46	30*	78	31*	16.5	21*					3.4	1307	127	8	16*	3	30	132
26	17*	35	14*	25	31*					4	1770	165	55	28*	10	20	82
28	18*	75	25*	37	42					2.7	1630	100	50	18	9	32	200
12	7.5*	25	10*	79	90					2.7	778	55	24	9.6	5	23	142
28	18*	56	22*	35	42*					4	1530	155	66	24*	8	23	83

* For bottom exposed packages, the I_D and P_D are calculated at 100°C, otherwise at 70°C.

* R_{DS(ON)} measured at V_{GS} other than 10V, 4.5V, 1.8V, 1.5V, or 1.2V.

* Q_g measured with V_{GS} = 10V. In all other cases V_{GS} = 4.5V.

Medium Voltage MOSFETs (Continued)

Part Number		Package	Configuration	Popular Application	Type	ESD Diode	Schottky Diode	Schottky Type	V _{DS} (V)	V _{GS} (±V)
AON6276		DFN 5x6	Single	SMPS	N	No	No		80	20
AON6278		DFN 5x6	Single	SMPS	N	No	No		80	20
AON6280		DFN 5x6	Single	SMPS	N	No	No		80	20
AON6282		DFN 5x6	Single	SMPS	N	No	No		80	20
AON6284		DFN 5x6	Single	SMPS	N	No	No		80	20
AON6284A		DFN 5x6	Single	SMPS	N	No	No		80	20
AON6448		DFN 5x6	Single	General Purpose	N	No	No		80	25
AON6242		DFN 5x6	Single	SMPS	N	No	No		60	20
AON6260		DFN 5x6	Single	SMPS	N	No	No		60	20
AON6262E		DFN 5x6	Single	SMPS	N	Yes	No		60	20
AON6264E		DFN 5x6	Single	SMPS	N	Yes	No		60	20
AON6268		DFN 5x6	Single	SMPS	N	No	No		60	20
AON6160		DFN 5x6	Single	SMPS	N	No	No		60	20
AON6162	NEW	DFN 5x6	Single	SMPS	N	No	No		60	20
AON6152		DFN 5x6	Single	SMPS	N	No	No		45	20
AON6154		DFN 5x6	Single	SMPS	N	No	No		45	20
AON6156		DFN 5x6	Single	SMPS	N	No	No		45	20
AON6144		DFN 5x6	Single	SMPS	N	No	No		40	20
AON6230		DFN 5x6	Single	SMPS	N	No	No		40	20
AON6234		DFN 5x6	Single	SMPS	N	No	No		40	20
AON6236		DFN 5x6	Single	SMPS	N	No	No		40	20
AON6240		DFN 5x6	Single	SMPS	N	No	No		40	20
AON6440		DFN 5x6	Single	General Purpose	N	No	No		40	20
AON6442		DFN 5x6	Single	General Purpose	N	No	No		40	20
AON6590		DFN 5x6	Single	General Purpose	N	No	No		40	20
AON6884		DFN 5x6	Dual	Inverter	N	No	No		40	20
AONS62602	NEW	DFN 5x6	Single	SMPS	N	No	No		60	20
AONS62614	NEW	DFN 5x6	Single	SMPS	N	No	No		60	20
AONS62922	NEW	DFN 5x6	Single	SMPS	N	No	No		120	20
AONS66402	NEW	DFN 5x6	Single	SMPS	N	No	No		40	20
SO-8										
AO4286		SO-8	Single	SMPS	N	No	No		100	20
AO4290A		SO-8	Single	SMPS	N	No	No		100	20
AO4292E		SO-8	Single	SMPS	N	Yes	No		100	20
AO4294A	NEW	SO-8	Single	SMPS	N	No	No		100	20
AO4296		SO-8	Single	SMPS	N	No	No		100	20
AO4482		SO-8	Single	Load Switch	N	No	No		100	20
AO4486		SO-8	Single	General Purpose	N	No	No		100	20
AO4892		SO-8	Dual	General Purpose	N	No	No		100	20
AO4260		SO-8	Single	SMPS	N	No	No		60	20
AO4262E		SO-8	Single	SMPS	N	Yes	No		60	20
AO4264E		SO-8	Single	SMPS	N	Yes	No		60	20
AO4268		SO-8	Single	SMPS	N	No	No		60	20
AO4450		SO-8	Single	Load Switch	N	No	No		40	20
AO4480		SO-8	Single	Display	N	Yes	No		40	20
AO4484		SO-8	Single	Inverter	N	No	No		40	20

1. Not recommended for new designs. Please contact your local sales office for a replacement part, if any.
2. On-resistance Static Source-Source, otherwise Static Drain-Source.

I _D (A)		P _D (W)			R _{DS(ON)} (mΩ max) at V _{GS} =						V _{GS(th)}	C _{iss}	C _{oss}	Cr _{ss}	Q _g	Q _{gd}	T _{rr}	Q _{rr}
25°C	70°C	25°C	70°C	10V	4.5V	2.5V	1.8V	1.5V	1.2V	(max V)	(pF)	(pF)	(pF)	(nC)	(nC)	(ns)	(nC)	
100	100*	215	86*	2.6						3.2	4940	770	40	68*	14	32	168	
85	66*	208	83*	3.3	4.6*					3.3	4646	632	31	61.5*	9.5	32	174	
85	65*	83	33*	4.1	5*					3.2	3930	592	66	58*	14	36	153	
85	56*	83	33*	5.6	8*					3.5	2848	392	22.5	36.5*	6	30	126	
78	49*	78	31*	7.1	10*					3.3	2162	300	16	28*	4.5	26	118	
48	42.5*	56	22*	6.5	8.5*					2.3	2540	310	18.5	16.5*	6	23	91	
65	41*	83	33*	9.6	12*					3.7	2600	340	120	44*	14	17	65	
85	66*	83	33*	3.6	4.5					2.5	5305	540	22	23	3	24.5	125	
85	67*	104	41.5*	2.4	3.5					2.5	5578	1390	75	37	12	30	130	
40	40*	48	19*	6.2	8.5					2.2	1650	520	52	15	6.5	19	60	
28	28*	37.5	15*	9.5	13.3					2.4	1100	300	28	7	3.5	19	65	
44	44*	56	22*	4.7	6.3					2.3	2520	670	65	21	8.5	22	80	
100	100*	215	86*	1.58						3.4	6485	1050	30	85	13	33	176	
100	100	215	86	2.1						3.2	4850	1700	130	70*	16	30	150	
100	100*	208	83*	1.15	1.85					2.3	7410	1120	75	37	5.5	25	71	
100	100*	125	50*	1.5	2.1					2.4	6575	870	82	38	16	22	60	
100	82*	78	31*	2.5	4					2.5	3975	545	62	23	16	19	43	
100	89*	78	31*	2.4	3.5					2.4	3780	675	60	22	16	17	45	
85	66*	104	42*	1.44	2.1					2.3	6050	1640	105	35	13	28	98	
85	67*	83	33*	3.4	5					2.4	2335	612	45	15	4.5	17.5	47.5	
30	24*	39	15.5*	7	10.5					2.4	1225	318	26.5	8.2	2.5	14	32.5	
85	67*	83	33*	1.6	2.4					2.4	5458	1395	103	31	10.8	23.9	84.6	
85	67*	83	33*	3.4	4.5					2.2	5000	780	300	40	15	16	38	
32	25*	35.7	14*	4.8	7					2.4	1830	521	43	12.8	6	16.5	40	
100	100*	208	83*	0.99	1.5					2.3	8320	1438	85	45	7	26	83	
34	21*	21	8*	11.3	13.8					2.7	1500	215	135	13.6	6.4	13	35	
85	85*	208	83*	2.5	3.6					2.5	5630	1510	95	35.5	9.5	27	113	
100	100*	119	47.5*	2.5	3.4					2.2	3660	1160	108	32	11.5	26	92	
85	75*	215	86*	7	9					2.4	3295	360	9	20	5.5	43	355	
85	85*	119	47.5*	1.6	2.3					2.3	5570	1035	75	33	5	21	65	
4	3	2.5	1.6	68	92					2.9	390	30	3	2.8	1.2	15	53	
15.5	12	3.1	2	6.4	7.6					2.3	4525	345	22.5	30	9	32	162	
8	6.2	3.1	2	23	33					2.7	1200	93	6.3	8	2.5	20	80	
11.5	9	3.1	2	12	15.5					2.5	2305	180	11.5	15.5	5	26.5	135	
13.5	10.5	3.1	2	8.3	10.6					2.3	3130	245	12.5	18.5	4.5	28	130	
6	5	3.1	2	37	42					2.7	1630	100	50	18	9	25	130	
4.2	3.4	3.1	2	79	90					2.7	778	55	24	8.1	4.1	21	94	
4	3	2	1.3	68	94					2.8	415	32	3	3	1.5	16	44	
18	14	3.1	2	5.2	6.3					2.3	4940	445	32	31	8.5	22	96	
16.5	13	3.1	2	6.5	8.5					2.2	1650	520	52	15	6.5	19	60	
13.5	10.5	3.1	2	9.8	13.5					2.4	1100	300	28	7	3.5	18.5	59	
19	14.5	3.1	2	4.8	6.5					2.3	2500	670	65	21	6.5	22	80	
7	5.5	3.1	2	30	38					3	516	82	43	4.3	1.4	18	10	
14	11	3.1	2	11.5	15.5					3	1600	320	100	10.5	4.8	31	33	
10	8	1.7	1.1	10	12.5					3	1500	215	135	13.6	6.4	30	19	

* For bottom exposed packages, the I_D and P_D are calculated at 100°C, otherwise at 70°C.

* R_{DS(ON)} measured at V_{GS} other than 10V, 4.5V, 1.8V, 1.5V, or 1.2V.

* Q_g measured with V_{GS} = 10V. In all other cases V_{GS} = 4.5V.

Medium Voltage MOSFETs (Continued)

Part Number	Package	Configuration	Popular Application	Type	ESD Diode	Schottky Diode	Schottky Type	V _{DS} (V)	V _{GS} (±V)
AO4443	SO-8	Single	Display	P	No	No		-40	20
AO4485	SO-8	Single	Inverter	P	No	No		-40	20
AO4421	SO-8	Single	General Purpose	P	No	No		-60	20
AO4441	SO-8	Single	Display	P	No	No		-60	20
AO4828	SO-8	Dual	General Purpose	N	No	No		60	20
AO4830 ⁽¹⁾	SO-8	Dual	Load Switch	N	No	No		80	30
AO4840	SO-8	Dual	General Purpose	N	No	No		40	20
AO4882	SO-8	Dual	Inverter	N	No	No		40	20
AO4884	SO-8	Dual	Inverter	N	No	No		40	20
AO4611	SO-8	Complementary	Inverter	N	No	No		60	20
AO4611	SO-8	Complementary	Inverter	P	No	No		-60	20
AO4612	SO-8	Complementary	Inverter	N	No	No		60	20
AO4612	SO-8	Complementary	Inverter	P	No	No		-60	20
AO4614B	SO-8	Complementary	Inverter	N	No	No		40	20
AO4614B	SO-8	Complementary	Inverter	P	No	No		-40	20
AOSD62666E	NEW	SO-8	Dual	Load Switch	N	No	No	60	20
Ultra SO-8									
AOL1482	Ultra SO-8	Single	Load Switch	N	No	No		100	20
AOL1240	Ultra SO-8	Single	General Purpose	N	No	No		40	20
AOL1242	Ultra SO-8	Single	General Purpose	N	No	No		40	20
AOL1454	Ultra SO-8	Single	Inverter	N	Yes	No		40	20
TO-220									
AOT9N40	TO-220	Single	General Purpose	N	No	No		400	30
AOT12N40	TO-220	Single	High Voltage	N	No	No		400	30
AOT12N30	TO-220	Single	High Voltage	N	No	No		300	30
AOT20N25	TO-220	Single	High Voltage	N	No	No		250	30
AOT254L	TO-220	Single	General Purpose	N	No	No		150	20
AOT2500L	TO-220	Single	General Purpose	N	No	No		150	20
AOT2502L	TO-220	Single	General Purpose	N	No	No		150	20
AOT290L	TO-220	Single	General Purpose	N	No	No		100	20
AOT292L	TO-220	Single	General Purpose	N	No	No		100	20
AOT296L	TO-220	Single	General Purpose	N	No	No		100	20
AOT410L	TO-220	Single	General Purpose	N	No	No		100	25
AOT412	TO-220	Single	General Purpose	N	No	No		100	25
AOT414	TO-220	Single	General Purpose	N	No	No		100	25
AOT418L	TO-220	Single	General Purpose	N	No	No		100	25
AOT2904	TO-220	Single	General Purpose	N	No	No		100	20
AOT2910L	TO-220	Single	General Purpose	N	No	No		100	20
AOT2916L	TO-220	Single	General Purpose	N	No	No		100	20
AOT280L	TO-220	Single	General Purpose	N	No	No		80	20
AOT282L	TO-220	Single	General Purpose	N	No	No		80	20
AOT284L	TO-220	Single	General Purpose	N	No	No		80	20
AOT286L	TO-220	Single	General Purpose	N	No	No		80	20
AOT288L	TO-220	Single	General Purpose	N	No	No		80	20
AOT480L	TO-220	Single	General Purpose	N	No	No		80	25

1. Not recommended for new designs. Please contact your local sales office for a replacement part, if any.
 2. On-resistance Static Source-Source, otherwise Static Drain-Source.

I _D (A)		P _D (W)			R _{DS(ON)} (mΩ max) at V _{GS} =						V _{GS(th)}	C _{iss}	C _{oss}	Cr _{ss}	Q _g	Q _{gd}	T _{rr}	Q _{rr}
25°C	70°C	25°C	70°C	10V	4.5V	2.5V	1.8V	1.5V	1.2V	(max V)	(pF)	(pF)	(pF)	(nC)	(nC)	(ns)	(nC)	
-6	-5	3.1	2	42	63					-2.6	940	97	72	8.4	4.3	17	11.5	
-10	-8	1.7	1.1	15	20					-2.5	2500	260	180	18.6	8.6	38	47	
-6.2	-5	3.1	2	40	50					-3	2417	179	120	22.7	9.2	34	47	
-4	-3.1	3.1	2	100	130					-3	930	85	35	8	3.2	27	32	
4.5	3.6	2	1.28	56	77					3	450	60	25	4.3	2.2	27.5	32	
3.5	2.9	2	1.3	75						5	640	40	20	5.5	1.2	20	50	
6	5	2	1.3	30	38					3	516	82	43	4.3	1.4	18	10	
8	6	2	1.3	19	27					2.4	415	112	11	3	1.1	12.5	3.5	
10	8	2	1.3	13	16					2.7	1500	215	135	13.6	6.4	13	35	
6.3	5	2	1.28	25	30					3	1920	155	116	24.2	14.4	33.2	43	
-4.9	-3.9	2	1.28	42	52					-3	2417	179	120	22.8	9.6	32	42	
4.5	3.6	2	1.28	56	77					3	450	60	25	4.3	2.2	27.5	32	
-3.2	-2.6	2	1.28	105	135					-3	930	85	35	8	3.2	27	32	
6	5	2	1.28	30	38					3	516	82	43	4.3	1.4	18	10	
-5	-4	2	1.28	45	63					-3	940	97	72	7.9	3.2	21	14	
9.5	7.5	2.5	1.6	14.5	19					2.2	755	220	20	6.5	3	15	45	
28	20*	75	37*	37	42					2.7	1630	100	50	18	9	32	200	
69	54*	125	62.5*	3	4.4					2.3	3165	920	45.5	18	3.5	20.5	56	
69	54*	68	34*	5.2	7.9					2.3	1350	405	26	8	2.3	15.5	31	
50	48*	60	30*	9	13					3	1600	320	100	10.5	4.8	31	33	
8	5*	132		800						4.5	630	73	5.7	13.1*	4.8	195	1900	
11	7*	184		590						4.5	925	100	6.4	17*	5.7	235	2400	
11.5	7.3*	132		420						4.5	632	90	7	12.8*	4.3	170	1300	
20	14*	208		170						4.5	1028	167	11	20*	8	179	1600	
32	22.5*	125	62.5*	46	53					2.7	2150	110	4	12	3	51	434	
152	107*	375	187.5*	6.5	7.6*					3.5	6460	586	22	97*	17	90	1090	
106	67*	277	111*	11						5.1	3010	345	14	43*	10	75	880	
140	110*	500	250*	3.5						4.1	7180	2780	42	90*	21	65	460	
105	82*	300	150*	4.5	5.3*					3.4	6775	557	32	90*	13.5	50	380	
70	50*	107	54*	10	12.5*					3.4	2785	238	12	16.5	5	35	210	
150	108*	333	167*	6.5	7.5*					4	6622	594	215	107*	40	27	177	
60	44*	150	75*	15.8	19.4*					3.8	2680	260	100	45	15	22	96	
43	31*	115	58*	25	31*					4	1770	165	55	28*	10	20	82	
105	82*	333	167*	10	12*					3.9	4334	382	131	69*	22	27	129	
120	120*	326	163*	4.4						3.3	7085	605	32	93	16	49	460	
30	21*	50	25*	24	33					2.7	1190	95	7	7	2.5	30	145	
23	16*	41.5	20.5*	34	43.5					2.7	870	68	3.5	5.5	2	20	88	
140	110*	333	166.5*	2.7	3.5*					3.4	11135	1315	80	160*	28	44	348	
105	82*	272.5	136*	3.5	5.2*					3.5	7765	960	66	58	21	40	320	
105	82*	250	125*	4.5	5.7*					3.3	5154	673	48	33.5	11.5	38	230	
70	55*	167	83*	6	7.9*					3.3	3142	435	43	44.5*	8	29	161	
46	36*	93.5	46.5*	9.2	12.5*					3.4	1871	265	14	26.5	4	32	162	
180	134*	333	167*	4.5	5.5*					4	6520	810	310	116*	38	28	132	

* For bottom exposed packages, the I_D and P_D are calculated at 100°C, otherwise at 70°C.

* R_{DS(ON)} measured at V_{GS} other than 10V, 4.5V, 1.8V, 1.5V, or 1.2V.

* Q_g measured with V_{GS} = 10V. In all other cases V_{GS} = 4.5V.

Medium Voltage MOSFETs (Continued)

Part Number	Package	Configuration	Popular Application	Type	ESD Diode	Schottky Diode	Schottky Type	V _{DS} (V)	V _{GS} (±V)
AOT482L	TO-220	Single	General Purpose	N	No	No		80	25
AOT270AL	TO-220	Single	General Purpose	N	No	No		75	20
AOT430	TO-220	Single	General Purpose	N	No	No		75	25
AOT470	TO-220	Single	General Purpose	N	No	No		75	25
AOT260L	TO-220	Single	General Purpose	N	No	No		60	20
AOT262L	TO-220	Single	General Purpose	N	No	No		60	20
AOT264L	TO-220	Single	General Purpose	N	No	No		60	20
AOT266L	TO-220	Single	General Purpose	N	No	No		60	20
AOT460	TO-220	Single	General Purpose	N	No	No		60	20
AOT1608L	TO-220	Single	Rugged Planar	N	No	No		60	20
AOT2606L	TO-220	Single	General Purpose	N	No	No		60	20
AOT2608L	TO-220	Single	General Purpose	N	No	No		60	20
AOT2610L	TO-220	Single	General Purpose	N	No	No		60	20
AOT2618L	TO-220	Single	General Purpose	N	No	No		60	20
AOT240L	TO-220	Single	General Purpose	N	No	No		40	20
AOT1404L	TO-220	Single	Rugged Planar	N	No	No		40	20
AOT2142L	TO-220	Single	General Purpose	N	No	No		40	20
TO-220F									
AOTF20N40	TO-220F	Single	High Voltage	N	No	No		400	30
AOTF12N30	TO-220F	Single	High Voltage	N	No	No		300	30
AOTF256L	TO-220F	Single	General Purpose	N	No	No		150	20
AOTF454L	TO-220F	Single	General Purpose	N	No	No		150	20
AOTF290L	TO-220F	Single	General Purpose	N	No	No		100	20
AOTF296L	TO-220F	Single	General Purpose	N	No	No		100	20
AOTF2910L	TO-220F	Single	General Purpose	N	No	No		100	20
AOTF2916L	TO-220F	Single	General Purpose	N	No	No		100	20
AOTF4126	TO-220F	Single	General Purpose	N	No	No		100	25
AOTF286L	TO-220F	Single	General Purpose	N	No	No		80	20
AOTF288L	TO-220F	Single	General Purpose	N	No	No		80	20
AOTF260L	TO-220F	Single	General Purpose	N	No	No		60	20
AOTF266L	TO-220F	Single	General Purpose	N	No	No		60	20
AOTF2606L	TO-220F	Single	General Purpose	N	No	No		60	20
AOTF2610L	TO-220F	Single	General Purpose	N	No	No		60	20
AOTF2618L	TO-220F	Single	General Purpose	N	No	No		60	20
AOTF240L	TO-220F	Single	General Purpose	N	No	No		40	20
AOTF2142L	TO-220F	Single	General Purpose	N	No	No		40	20
AOTF4185	TO-220F	Single	General Purpose	P	No	No		-40	20
AOTF409	TO-220F	Single	General Purpose	P	No	No		-60	20
TO-247									
AOK40N30	TO-247	Single	General Purpose	N	No	No		300	30

1. Not recommended for new designs. Please contact your local sales office for a replacement part, if any.
 2. On-resistance Static Source-Source, otherwise Static Drain-Source.

I _D (A)		P _D (W)		R _{DS(ON)} (mΩ max) at V _{GS} =						V _{GS(th)}	C _{iss}	C _{oss}	C _{rss}	Q _g	Q _{gd}	T _{rr}	Q _{rr}
25°C	70°C	25°C	70°C	10V	4.5V	2.5V	1.8V	1.5V	1.2V	(max V)	(pF)	(pF)	(pF)	(nC)	(nC)	(ns)	(nC)
105	82*	333	167*	7.2	9*					3.7	4054	458	160	66.8*	20.2	26	108
140	110*	500	250*	2.6	3.2*					3.3	10830	1520	97	147*	30	53	438
80	78*	268	134*	11.5						4	4700	400	180	114*	18	53	143
100	78*	268	134*	10.5						4	4700	400	180	114*	18	53	143
140	110*	330	165*	2.5	2.9*					3.2	11800	1360	40	150*	15	32	200
140	110*	333	167*	3	3.2*					3.2	8140	1040	32	95*	5	30	185
140	110*	333	167*	3.2	3.5*					3.2	6960	840	30	75*	5	26	155
140	110*	268	134*	3.5	4*					3.2	5650	720	20	65*	7	27	145
85	85*	268	134*	7.5						4	3800	430	190	33	19	53	98
140	100*	333	166*	7.6						3.7	3069	721	56	69	21	40	355
72	56*	115	57.5*	6.5						3.5	4050	345	16.8	22	5	26	125
72	54*	100	50*	8						3.6	2995	270	10.5	38.5*	3.5	24	115
55	39*	75	37.5*	10.7	13.5					2.5	2007	177	12.5	8.5	2.2	19	69.5
23	18*	41.5	20.5*	19	25					2.5	950	108	7	6	1.6	20	70
105	82*	176	88*	2.9	3.7					2.2	3510	1070	68	22	7	21	58
220	157*	417	208*	4.2						3.7	3568	1388	151	71	23	45	287
120	120	312	156	1.9	2.5					2.3	8320	1438	85	45	7	26	83
20	13*	50		250						4.3	1898	212	15	37*	12	285	3900
11.5	7.3*	36		420						4.5	632	90	7	12.8*	4.3	170	1300
12	8.5*	33	16*	85	100					2.8	1165	61.5	2.5	7	1.2	37	265
13	8*	41	16*	94	100*					4.6	820	70	22	15	4.4	32.5	230
72	58*	48	24*	4.2						4.1	7180	2780	42	90*	21	65	460
41	29*	36.5	18*	10	12.5*					3.4	2785	238	12	37*	5	35	210
22	15.5*	27	13.5*	24	33					2.7	1190	95	7	7	2.5	30	145
17	12*	23.5	11.5*	34	43					2.7	870	68	3.5	5.5	2	20	88
27	19*	42	21*	24	30*					4	1770	165	55	28*	10	20	82
56	39*	37.5	18.5*	6	8*					3.3	3142	435	43	44.5*	8	29	161
43	30*	35.5	17.5*	9.2	12.5*					3.4	1871	265	14	26.5	4	32	162
92	66.5*	46.5	23.5*	2.6	3*					3.2	11800	1360	40	150*	15	32	200
78	55*	45.5	22.5*	3.5	4*					3.2	5650	720	20	65*	7	27	145
54	38*	36.5	18*	6.5						3.5	4050	345	16.8	22	5	26	125
35	25*	31	15.5*	10.7	13.5					2.5	2007	177	12.5	8.5	2.2	19	69.5
22	16*	23.5	11.5*	19	25					2.5	950	108	7	6	1.6	20	70
85	60*	41	20*	2.9	3.7					2.2	3510	1070	68	22	7	21	58
112	78*	41	20*	1.9	2.5					2.3	8320	1438	85	45	7	26	83
-34	-27*	33	16*	16	20					-2.5	2550	280	190	18.6	8.6	25	75
-24	-17*	43	21*	40	54					-2.4	2461	178	120	19.7	8.9	26.68	167.12
40	25*	357		85						4.1	2718	405	31	60*	21	275	8200

* For bottom exposed packages, the I_D and P_D are calculated at 100°C, otherwise at 70°C.

* R_{DS(ON)} measured at V_{GS} other than 10V, 4.5V, 1.8V, 1.5V, or 1.2V.

* Q_g measured with V_{GS} = 10V. In all other cases V_{GS} = 4.5V.

Medium Voltage MOSFETs (Continued)

Part Number	Package	Configuration	Popular Application	Type	ESD Diode	Schottky Diode	Schottky Type	V _{DS} (V)	V _{GS} (±V)
TO-251A									
AOI5N40	TO-251A	Single	High Voltage	N	No	No		400	30
AOI468	TO-251A	Single	General Purpose	N	No	No		300	30
AOI8N25	TO-251A	Single	General Purpose	N	No	No		250	30
AOI294A	TO-251A	Single	General Purpose	N	No	No		100	20
AOI296A	TO-251A	Single	General Purpose	N	No	No		100	20
AOI478	TO-251A	Single	General Purpose	N	No	No		100	20
AOI4126	TO-251A	Single	General Purpose	N	No	No		100	25
AOI4286	TO-251A	Single	General Purpose	N	No	No		100	20
AOI442	TO-251A	Single	General Purpose	N	No	No		60	20
AOI444	TO-251A	Single	General Purpose	N	No	No		60	20
AOI2610E	TO-251A	Single	General Purpose	N	No	No		60	20
AOI4130	TO-251A	Single	General Purpose	N	No	No		60	20
AOI4184	TO-251A	Single	Load Switch	N	No	No		40	20
AOI4185	TO-251A	Single	General Purpose	N	No	No		-40	20
AOI409	TO-251A	Single	General Purpose	N	No	No		-60	20
TO-252									
AOD3N40	TO-252	Single	High Voltage	N	No	No		400	30
AOD3T40P	TO-252	Single	High Voltage	N	No	No		400	30
AOD5N40	TO-252	Single	High Voltage	N	No	No		400	30
AOD5T40P	TO-252	Single	High Voltage	N	No	No		400	30
AOD9N40	TO-252	Single	General Purpose	N	No	No		400	30
AOD9T40P	TO-252	Single	General Purpose	N	No	No		400	30
AOD468	TO-252	Single	General Purpose	N	No	No		300	30
AOD458	TO-252	Single	General Purpose	N	No	No		250	30
AOD8N25	TO-252	Single	High Voltage	N	No	No		250	30
AOD450	TO-252	Single	Inverter	N	No	No		200	30
AOD2210	TO-252	Single	General Purpose	N	No	No		200	20
AOD4504	TO-252	Single	General Purpose	N	No	No		200	20
AOD256	TO-252	Single	General Purpose	N	No	No		150	20
AOD2544	TO-252	Single	General Purpose	N	No	No		150	20
AOD4454	TO-252	Single	General Purpose	N	No	No		150	20
AOD464	TO-252	Single	General Purpose	N	No	No		105	25
AOD478	TO-252	Single	General Purpose	N	No	No		100	20
AOD482	TO-252	Single	General Purpose	N	No	No		100	20
AOD294A	TO-252	Single	General Purpose	N	No	No		100	20
AOD296A	TO-252	Single	General Purpose	N	No	No		100	20
AOD2910	TO-252	Single	General Purpose	N	No	No		100	20
AOD2910E	TO-252	Single	General Purpose	N	Yes	No		100	20
AOD2916	TO-252	Single	General Purpose	N	No	No		100	20
AOD2922	TO-252	Single	General Purpose	N	No	No		100	20
AOD4126	TO-252	Single	General Purpose	N	No	No		100	25
AOD4286	TO-252	Single	General Purpose	N	No	No		100	20
AOD2810	TO-252	Single	General Purpose	N	No	No		80	20
AOD2816	TO-252	Single	General Purpose	N	No	No		80	20

1. Not recommended for new designs. Please contact your local sales office for a replacement part, if any.
2. On-resistance Static Source-Source, otherwise Static Drain-Source.

I _D (A)		P _D (W)		R _{DS(ON)} (mΩ max) at V _{GS} =						V _{GS(th)}	C _{iss}	C _{oss}	Cr _{ss}	Q _g	Q _{gd}	T _{rr}	Q _{rr}
25°C	70°C	25°C	70°C	10V	4.5V	2.5V	1.8V	1.5V	1.2V	(max V)	(pF)	(pF)	(pF)	(nC)	(nC)	(ns)	(nC)
4.2	2.8*	78		1600						4.5	331	42	3	6.9*	2.3*	160	930
11.5	8.3*	150		420						4.5	632	90	7	12.8*	4.3*	170	1300
8	5*	78		560						4.3	306	51	3.2	6*	1.5*	77	290
55	35*	73	30*	12	15.5					2.5	2305	180	11.5	15.5	5	29.5	160
70	45*	89	35*	8.3	10.6					2.3	3130	245	12.5	18.5	4.5	30	150
11	8*	45	23*	140	152					2.8	445	29	16	5.1	2.4	21	97
43	30*	100	50*	24	30*					4	1770	165	55	28*	10	20	82
14	10*	30	15*	68	92					2.9	390	30	3	2.8	1.2	15	53
37	26*	60	30*	20	25					2.7	1920	155	116	24.2	14.4	34	46
12	9*	20	10*	60	85					3	450	61	27	3.8	1.9	27	30
46	36.5	59.5	23.5*	9.5						2.4	1100	300	28	7	3.5	19	65
30	20*	52	25*	24	30					2.8	1582	100	67	13.4	7.2	22	76
50	40*	50	25*	8	11					3	1500	215	135	27.2	6.4	29	26
-40	-31*	62.5	31*	15*	20*					-3	2550	280	190	18.6	8.6	38	47
-26	-18*	60	30*	40*	55*					-2.4	2977	241	153	22.2	10	40	59
2.6	1.6*	50		3100						4.5	186	26	2.1	4.2*	1	140	640
2	1.3*	35		3300						5	139	9	1.3	3*	0.6	135	700
4.2	2.8*	78		1600						4.5	331	42	3	6.9*	2.3	160	930
3.9	2.5*	52		1450						5	273	16	1.5	5*	1.4	172	1100
8	5*	125		800						4.5	962	73	8	19.5*	7.1	195	1900
6.6	4.2*	83		800						5	530	30	2.8	9*	1.8	233	2100
11.5	8.3*	150		420						4.5	632	90	7	12.8*	4.3	170	1300
14	10*	150		280						4.5	637	104	7.1	12	4.6	150	1240
8	5*	78		560						4.3	306	51	3.2	6*	1.5	77	290
3.8	2.7*	25	12.5*	700						6	215	32	7.2	3.82*	1.47	59	142
18	13*	100	50*	105	120*					2.5	2065	74	3.8	12	3	60	800
6	4.5*	42.5	21*	400						3.7	328	20.5	8	44	30	35	150
19	13.5*	83	41.5*	85	100					2.8	1165	61.5	2.5	7	1.2	37	265
23	16*	75	37.5*	54	66					2.7	675	78	4	5.5	2.5	37	210
20	14*	100	50*	94	110*					4.6	820	70	22	15*	4.4	32.5	230
40	28*	100	50*	28	31*					4	2038	204	85	38.5*	10	59.6	161
11	8*	45	23*	140	152					2.8	445	29	16	5.1	2.4	21	97
32	22*	100	50*	37	42					2.7	1630	100	50	18	9	32	200
55	35*	73	30*	12	15.5					2.5	2305	180	11.5	15.5	5	29.5	160
70	45*	89	35*	8.3	10.6					2.3	3130	245	12.5	18.5	4.5	30	150
31	21.5*	53.5	26.5*	24	33					2.7	1190	95	7	7	2.5	30	145
37	26*	71.5	35.5*	23	33					2.7	1200	93	6.3	8	2.5	25	120
25	18*	50	25*	34	43.5					2.7	870	68	3.5	5.5	2	20	88
7	5*	17	8.5*	140	176					2.7	250	19	2.5	1.8	0.8	19	52
43	30*	100	50*	24	30*					4	1770	165	55	28*	10	20	82
14	10*	30	15*	68	92					2.9	390	30	3	2.8	1.2	15	53
46	36*	100	50*	8.5	12*					3.4	1871	265	14	26.5*	4	32	162
35	27*	53.5	26.5*	15	29*					3.5	1109	154	9	5	3.2	30	122

* For bottom exposed packages, the I_D and P_D are calculated at 100°C, otherwise at 70°C.

* R_{DS(ON)} measured at V_{GS} other than 10V, 4.5V, 1.8V, 1.5V, or 1.2V.

* Q_g measured with V_{GS} = 10V. In all other cases V_{GS} = 4.5V.

Medium Voltage MOSFETs (Continued)

Part Number	Package	Configuration	Popular Application	Type	ESD Diode	Schottky Diode	Schottky Type	V _{DS} (V)	V _{GS} (±V)
AOD474B	TO-252	Single	General Purpose	N	No	No		75	20
AOD442	TO-252	Single	General Purpose	N	No	No		60	20
AOD444	TO-252	Single	General Purpose	N	No	No		60	20
AOD2606	TO-252	Single	General Purpose	N	No	No		60	20
AOD2610E	TO-252	Single	General Purpose	N	Yes	No		60	20
AOD4130	TO-252	Single	General Purpose	N	No	No		60	20
AOD240	TO-252	Single	SMPS	N	No	No		40	20
AOD242	TO-252	Single	General Purpose	N	No	No		40	20
AOD454A	TO-252	Single	General Purpose	N	No	No		40	20
AOD486A	TO-252	Single	Inverter	N	Yes	No		40	20
AOD4184A	TO-252	Single	Inverter	N	No	No		40	20
AOD4186	TO-252	Single	Inverter	N	No	No		40	20
AOD413A	TO-252	Single	General Purpose	P	No	No		-40	20
AOD4185	TO-252	Single	General Purpose	P	No	No		-40	20
AOD4189	TO-252	Single	Inverter	P	No	No		-40	20
AOD407	TO-252	Single	General Purpose	P	No	No		-60	20
AOD409	TO-252	Single	General Purpose	P	No	No		-60	20
AOD603A	TO-252	Complementary	Inverter	N	No	No		60	20
AOD603A	TO-252	Complementary	Inverter	P	No	No		-60	20
AOD609	TO-252	Complementary	Inverter	N	No	No		40	20
AOD609	TO-252	Complementary	Inverter	P	No	No		-40	20
TO-262									
AOW2502	TO-262	Single	General Purpose	N	No	No		150	20
AOW292	TO-262	Single	General Purpose	N	No	No		100	20
AOW284	TO-262	Single	General Purpose	N	No	No		80	20
AOW482	TO-262	Single	General Purpose	N	No	No		80	25
TO-262F									
AOWF412	TO-262F	Single	General Purpose	N	No	No		100	25
TO-263									
AOB254L	TO-263	Single	General Purpose	N	No	No		150	20
AOB256L	TO-263	Single	General Purpose	N	No	No		150	20
AOB2500L	TO-263	Single	General Purpose	N	No	No		150	20
AOB2502L	TO-263	Single	General Purpose	N	No	No		150	20
AOB290L	TO-263	Single	General Purpose	N	No	No		100	20
AOB292L	TO-263	Single	General Purpose	N	No	No		100	20
AOB410L	TO-263	Single	General Purpose	N	No	No		100	25
AOB414	TO-263	Single	General Purpose	N	No	No		100	25
AOB416	TO-263	Single	General Purpose	N	No	No		100	25
AOB2904	TO-263	Single	General Purpose	N	No	No		100	20
AOB280L	TO-263	Single	General Purpose	N	No	No		80	20
AOB282L	TO-263	Single	General Purpose	N	No	No		80	20
AOB284L	TO-263	Single	General Purpose	N	No	No		80	20
AOB286L	TO-263	Single	General Purpose	N	No	No		80	20
AOB288L	TO-263	Single	General Purpose	N	No	No		80	20

1. Not recommended for new designs. Please contact your local sales office for a replacement part, if any.
2. On-resistance Static Source-Source, otherwise Static Drain-Source.

I _D (A)		P _D (W)			R _{DS(ON)} (mΩ max) at V _{GS} =						VGS(th)	Ciss	Coss	Crss	Qg	Qgd	Trr	Qrr
25°C	70°C	25°C	70°C	10V	4.5V	2.5V	1.8V	1.5V	1.2V	(max V)	(pF)	(pF)	(pF)	(nC)	(nC)	(ns)	(nC)	
10	7*	28.5	14.5*	132	155					2.3	282	30	12	3.2	1.7	15	60	
38	26*	60	30*	20	25					3	1920	155	116	24.2	14.4	34	46	
12	9*	20	10*	60	85					3	450	61	27	3.8	1.9	27	30	
46	36*	150	75*	6.8						3.5	4050	345	16.8	22	5	26	125	
46	36.5*	59.5	23.5*	9.5	13.3					2.4	1100	300	28	7	3.5	19	65	
30	20*	52	25*	24	30					2.8	1582	100	67	13.4	7.2	22	76	
70	55*	150	75*	3	3.9					2.2	3510	1070	68	22	7	21	58	
54	42*	53.5	26.5*	5.8	8.2					2.3	1350	405	26	8	2.3	15.5	31	
20	15*	37	18*	30	40					3	516	82	43	8.3	1.6	18	10	
50	36*	50	25*	9.8	13					3	1600	320	100	10.5	4.8	31	33	
50	40*	50	25*	7	9.5					2.6	1500	215	135	14	6	29	26	
35	27*	50	25*	15	19					2.7	980	130	80	9	4.5	12	31	
-12	-12*	50	25*	44	66					-3	900	97	68	7.2	3.5	21.2	13.8	
-40	-31*	62.5	31*	15	20					-3	2550	280	190	18.6	8.5	38	47	
-40	-28*	62.5	31*	22	29					-3	1870	185	155	7.9	6.2	32	30	
-12	-10*	50	25*	115	150					-3	987	114	46	7.4	3.5	27.5	30	
-26	-18*	60	30*	40	55					-2.4	2977	241	153	22.2	10	40	59	
12	9.5*	27	13.5*	60	85					3	450	61	27	3.8	1.9	27	30	
-12	-9.5*	42.5	21.5*	115	150					-3	960	86	38	7.4	3.5	27.5	30	
12	12*	27	14*	30	40					3	516	82	43	8.3	1.6	18	10	
-12	-12*	30	15*	45	66					-3	900	97	68	7.2	3.5	21	14	
106	67*	277	111*	10.7						5.1	3010	345	14	43*	10	75	880	
105	105*	300	150*	4.1	4.9*					3.4	6775	557	32	90*	13.5	50	380	
105	82*	250	125*	4.3	5.5*					3.3	5154	673	48	71*	11.5	38	230	
105	82*	333	167*	7.2	9*					3.7	4054	458	160	66.8*	20.2	26	108	
30	20*	33	16*	15.8	19.4*					3.8	2680	260	100	45	15	22	96	
32	22.5*	125	62.5*	46	53					2.7	2150	110	4	12	3	51	434	
19	13.5*	83	41.5*	85	100					2.8	1165	61.5	2.5	7	1.2	37	265	
152	107*	375	187.5*	6.2	7.3*					3.5	6460	586	22	97*	17	90	1090	
106	67*	277	111*	10.7						5.1	3010	347	14	43*	10	75	880	
140	110*	500	250*	3.2						4.1	7180	2780	42	90*	21	65	460	
105	82*	300	150*	4.1						3.4	6775	557	32	90*	13.5	50	380	
150	108*	333	167*	6.2						4	6622	594	215	107*	40	27	177	
51	36*	150	75*	25						4	1770	165	55	28*	10	20	82	
45	32*	150	75*	36	43*					4	1180	110	36	20*	6.3	19	70	
120	120*	326	163*	4.4						3.3	7085	605	32	93	16	49	460	
140	110*	333	166.5*	2.2	3.1*					3.4	11135	1315	80	160*	28	44	348	
105	82*	272.5	136*	3.2	4.9*					3.5	7765	960	66	58	21	40	320	
105	82*	250	125*	4.3	5.5*					3.3	5154	673	48	33.5	11.5	38	230	
70	55*	167	83*	5.7	7.6*					3.3	3142	435	43	44.5*	8	29	161	
46	36*	93.5	46.5*	8.9	12.2*					3.4	1871	265	14	26.5	4	32	162	

* For bottom exposed packages, the I_D and P_D are calculated at 100°C, otherwise at 70°C.

* R_{DS(ON)} measured at V_{GS} other than 10V, 4.5V, 1.8V, 1.5V, or 1.2V.

* Qg measured with V_{GS} = 10V. In all other cases V_{GS} = 4.5V.

Medium Voltage MOSFETs (Continued)

Part Number	Package	Configuration	Popular Application	Type	ESD Diode	Schottky Diode	Schottky Type	V _{DS} (V)	V _{GS} (±V)
AOB270AL	TO-263	Single	General Purpose	N	No	No		75	20
AOB470L	TO-263	Single	General Purpose	N	No	No		75	25
AOB260L	TO-263	Single	General Purpose	N	No	No		60	20
AOB266L	TO-263	Single	General Purpose	N	No	No		60	20
AOB1608L	TO-263	Single	Rugged Planar	N	No	No		60	20
AOB2606L	TO-263	Single	General Purpose	N	No	No		60	30
AOB2608L	TO-263	Single	Rugged Planar	N	No	No		60	20
AOB240L	TO-263	Single	General Purpose	N	No	No		40	20
AOB1404L	TO-263	Single	Rugged Planar	N	No	No		40	20
AOB4184	TO-263	Single	Load Switch	N	No	No		40	20
AOB409L	TO-263	Single	General Purpose	P	No	No		-60	20
AOB411L	TO-263	Single	General Purpose	P	No	No		-60	20

1. Not recommended for new designs. Please contact your local sales office for a replacement part, if any.
 2. On-resistance Static Source-Source, otherwise Static Drain-Source.

I _D (A)		P _D (W)		R _{DS(ON)} (mΩ max) at V _{GS} =						VGS(th)	Ciss	Coss	Crss	Qg	Qgd	Trr	Qrr
25°C	70°C	25°C	70°C	10V	4.5V	2.5V	1.8V	1.5V	1.2V	(max V)	(pF)	(pF)	(pF)	(nC)	(nC)	(ns)	(nC)
140	110*	500	250*	2.4	3*					3.3	10830	1520	97	147*	30	53	438
100	78*	268	134*	10.2						4	4700	400	180	114*	18	53	143
140	110*	330	165*	2.2	2.5*					3.2	11800	1360	40	150*	15	32	200
140	110*	268	134*	3.2	3.8*					3.2	5650	720	20	65*	7	27	145
140	100*	333	166*	7.3						3.7	3069	721	56	69	21	40	355
72	56*	115	57.5*	6.2						3.5	4050	345	16.8	22	5	26	125
72	54*	100	50*	7.6						3.6	2995	270	10.5	38.5*	3.5	24	115
105	82*	176	88*	2.6	3.5					2.2	3510	1070	68	22	7	21	58
220	157*	417	208*	3.9						3.7	3568	1388	151	71	23	45	287
50	24*	50	25*	10	13					3	1500	215	135	13.6	6.4	19	59
-31.5	-22*	83.3	41.6*	38	50					-2.4	2461	178	120	19.7	8.9	25.7	167
-78	-55*	187	93*	16.5	22					-2.5	5330	483	234	40	18	27	165

* For bottom exposed packages, the I_D and P_D are calculated at 100°C, otherwise at 70°C.

* R_{DS(ON)} measured at V_{GS} other than 10V, 4.5V, 1.8V, 1.5V, or 1.2V.

* Qg measured with V_{GS} = 10V. In all other cases V_{GS} = 4.5V.

High Voltage MOSFETs

Part Number	Package	Configuration	Popular Application	Type	ESD Diode	Schottky Diode	Schottky Type	V _{DS} (V)	V _{GS} (±V)
V_{DS} = 500V									
AOK29S50	TO-247	Single	High Voltage	N	No	No		500	30
AOTF29S50	TO-220F	Single	High Voltage	N	No	No		500	30
AOW29S50	TO-262	Single	High Voltage	N	No	No		500	30
V_{DS} = 600V									
AOB11S60	TO-263	Single	High Voltage	N	No	No		600	30
AOB15S60	TO-263	Single	High Voltage	N	No	No		600	30
AOB27S60	TO-263	Single	High Voltage	N	No	No		600	30
AOB42S60	TO-263	Single	High Voltage	N	No	No		600	30
AOB4S60	TO-263	Single	High Voltage	N	No	No		600	30
AOB7S60	TO-263	Single	High Voltage	N	No	No		600	30
AOD11S60	TO-252	Single	High Voltage	N	No	No		600	30
AOD4S60	TO-252	Single	High Voltage	N	No	No		600	30
AOD7S60	TO-252	Single	High Voltage	N	No	No		600	30
AOI11S60	TO-251A	Single	High Voltage	N	No	No		600	30
AOI4S60	TO-251A	Single	High Voltage	N	No	No		600	30
AOI4T60	TO-251A	Single	High Voltage	N	No	No		600	30
AOI4T60P	TO-251A	Single	High Voltage	N	No	No		600	30
AOK53S60	TO-247	Single	High Voltage	N	No	No		600	30
AOT15S60	TO-220	Single	High Voltage	N	No	No		600	30
AOT4S60	TO-220	Single	High Voltage	N	No	No		600	30
AOT7S60	TO-220	Single	High Voltage	N	No	No		600	30
AOTF11S60	TO-220F	Single	High Voltage	N	No	No		600	30
AOTF15S60	TO-220F	Single	High Voltage	N	No	No		600	30
AOTF42S60	TO-220F	Single	High Voltage	N	No	No		600	30
AOTF42S60L	TO-220F	Single	High Voltage	N	No	No		600	30
AOTF4S60	TO-220F	Single	High Voltage	N	No	No		600	30
AOTF7S60	TO-220F	Single	High Voltage	N	No	No		600	30
AOTF11N62	TO-220F	Single	High Voltage	N	No	No		620	30
AOU4S60	TO-251	Single	High Voltage	N	No	No		600	30
AOV11S60	DFN8x8	Single	High Voltage	N	No	No		600	30
AOV15S60	DFN8x8	Single	High Voltage	N	No	No		600	30
AOV20S60	DFN8x8	Single	High Voltage	N	No	No		600	30
AOW11S60	TO-262	Single	High Voltage	N	No	No		600	30
AOW15S60	TO-262	Single	High Voltage	N	No	No		600	30
AOW20S60	TO-262	Single	High Voltage	N	No	No		600	30
AOW4S60	TO-262	Single	High Voltage	N	No	No		600	30
AOW7S60	TO-262	Single	High Voltage	N	No	No		600	30
AOWF11S60	TO-262F	Single	High Voltage	N	No	No		600	30
AOWF15S60	TO-262F	Single	High Voltage	N	No	No		600	30
AOWF20S60	TO-262F	Single	High Voltage	N	No	No		600	30
AOWF4S60	TO-262F	Single	High Voltage	N	No	No		600	30
AOWF7S60	TO-262F	Single	High Voltage	N	No	No		600	30

1. Not recommended for new designs. Please contact your local sales office for a replacement part, if any.
2. On-resistance Static Source-Source, otherwise Static Drain-Source.

I _D (A)		P _D (W)		R _{DS(ON)} (mΩ max) at V _{GS} =						V _{GS(th)}	C _{iss}	C _{oss}	C _{rss}	Q _g	Q _{gd}	T _{rr}	Q _{rr}
25°C	70°C	25°C	70°C	10V	4.5V	2.5V	1.8V	1.5V	1.2V	(max V)	(pF)	(pF)	(pF)	(nC)	(nC)	(ns)	(nC)
29	18*	357		150						3.9	1312	88	2.5	26.6*	9.2	387	7300
29	18*	50		150						3.9	1312	88	2.5	26.6*	9.2	387	7300
29	18*	357		150						3.9	1312	88	2.5	26.6*	9.2	387	7300
11	8*	178		399						4.1	545	37.3	1.42	11*	3.8	250	3300
15	10*	208		290						3.8	717	58	1.3	15.6*	6	282	4500
27	17*	357		160						4	1294	80	2.3	26*	8.8	440	7500
37	23*	417		109						3.8	2154	135	2.7	40*	11.9	473	10500
4	3.7*	83		900						4.1	263	21	0.75	6*	1.8	177	1500
7	5*	104		600						3.9	372	28	1.2	8.2*	2.8	198	2400
11	8.5*	208		399						4.1	545	37.3	1.42	11*	3.8	250	3300
4	3*	56.8		900						4.1	263	21	0.75	6*	1.8	177	1500
7	5*	83		600						3.9	372	28	1.2	8.2*	2.8	198	2400
11	8.5*	208		399						4.1	545	37.3	1.42	11*	3.8	250	3300
4	3*	56.8		900						4.1	263	21	0.75	6*	1.8	177	1500
4	2.5*	83		2100						5	460	22	3.5	9*	2.4	384	3900
4	2.5*	83		2100						5	460	22	3.5	9*	2.4	384	3900
53	33*	520		70						3.8	3034	222	3	59*	19	664	14000
15	10*	208		290						3.8	717	58	1.3	15.6*	6	282	4500
4	3.7*	83		900						4.1	263	21	0.75	6*	1.8	177	1500
7	5*	104		600						3.9	372	28	1.2	8.2*	2.8	198	2400
11	8*	38		399						4.1	545	37.3	1.42	11*	3.8	250	3300
15	10*	27.8		290						3.8	717	58	1.3	15.6*	6	282	4500
39	25*	50		99						3.8	2154	135	2.7	40*	11.9	473	10500
39	25*	37.9		99						3.8	2154	135	2.7	40*	11.9	473	10500
4	3.7*	83		900						4.1	263	21	0.75	6*	1.8	177	1500
7	5*	34		600						3.9	372	28	1.2	8.2*	2.8	198	2400
11	8*	50		650						4.5	1656	146	11.2	30.6*	9.6	500	5900
4	3*	56.8		900						4.1	263	21	0.75	6*	1.8	177	1500
8	7*	156		500						4.1	545	37.3	1.42	11*	3.8	250	3300
12	9.4*	208		360						3.8	717	58	1.3	15.6*	6	282	4500
18	13*	276		250						4.1	1038	68	2.1	20*	7.6	350	5700
11	8*	178		399						4.1	545	37.3	1.42	11*	3.8	250	3300
15	10*	208		290						3.8	717	58	1.3	15.6*	6	282	4500
20	14*	266		199						4.1	1038	68	2.1	19.8*	7.6	350	5700
4	3.7*	83		900						4.1	263	21	0.75	6*	1.8	177	1500
7	5*	104		600						3.9	372	28	1.2	8.2*	2.8	198	2400
11	8*	28		399						4.1	545	37.3	1.42	11*	3.8	250	3300
15	10*	27.8		290						3.8	717	58	1.3	15.6*	6	282	4500
20	14*	28		199						4.1	1038	68	2.1	19.8*	7.6	350	5700
4	3.7*	83		900						4.1	263	21	0.75	6*	1.8	177	1500
7	5*	25		600						3.9	372	28	1.2	8.2*	2.8	198	2400

* For bottom exposed packages, the I_D and P_D are calculated at 100°C, otherwise at 70°C.

* R_{DS(ON)} measured at V_{GS} other than 10V, 4.5V, 1.8V, 1.5V, or 1.2V.

* Q_g measured with V_{GS} = 10V. In all other cases V_{GS} = 4.5V.

High Voltage MOSFETs (Continued)

Part Number	Package	Configuration	Popular Application	Type	ESD Diode	Schottky Diode	Schottky Type	V _{DS} (V)	V _{GS} (±V)
V_{DS} = 650V									
AOB11S65	TO-263	Single	High Voltage	N	No	No		650	30
AOB15S65	TO-263	Single	High Voltage	N	No	No		650	30
AOB25S65	TO-263	Single	High Voltage	N	No	No		650	30
AOB7S65	TO-263	Single	High Voltage	N	No	No		650	30
AOD7S65	TO-252	Single	High Voltage	N	No	No		650	30
AOI7S65	TO-251A	Single	High Voltage	N	No	No		650	30
AOT11S65	TO-220	Single	High Voltage	N	No	No		650	30
AOT25S65	TO-220	Single	High Voltage	N	No	No		650	30
AOTF11S65	TO-220F	Single	High Voltage	N	No	No		650	30
AOTF15S65	TO-220F	Single	High Voltage	N	No	No		650	30
AOTF25S65	TO-220F	Single	High Voltage	N	No	No		650	30
AOTF7S65	TO-220F	Single	High Voltage	N	No	No		650	30
AOU7S65	TO-251	Single	High Voltage	N	No	No		650	30
AOW11S65	TO-262	Single	High Voltage	N	No	No		650	30
AOW15S65	TO-262	Single	High Voltage	N	No	No		650	30
AOW25S65	TO-262	Single	High Voltage	N	No	No		650	30
AOW7S65	TO-262	Single	High Voltage	N	No	No		650	30
AOWF11S65	TO-262F	Single	High Voltage	N	No	No		650	30
AOWF15S65	TO-262F	Single	High Voltage	N	No	No		650	30
AOWF25S65	TO-262F	Single	High Voltage	N	No	No		650	30
AOWF7S65	TO-262F	Single	High Voltage	N	No	No		650	30

αMOS5™ High Voltage MOSFETs

Part Number	Package	Configuration	Popular Application	Type	ESD Diode	Schottky Diode	Schottky Type	V _{DS} (V)	V _{GS} (±V)
V_{DS} = 600V									
AOTF190A60L	<i>NEW</i>	TO-220F	Single	High Voltage	N	No	No	600	20

1. Not recommended for new designs. Please contact your local sales office for a replacement part, if any.
 2. On-resistance Static Source-Source, otherwise Static Drain-Source.

I _D (A)		P _D (W)		10V	R _{DS(ON)} (mΩ max) at V _{GS} =					VGS(th) (max V)	Ciss (pF)	Coss (pF)	Crss (pF)	Qg (nC)	Qgd (nC)	Trr (ns)	Qrr (nC)
25°C	70°C	25°C	70°C		4.5V	2.5V	1.8V	1.5V	1.2V								
11	8*	198		399						4	646	42	1.1	13.2*	4.3	278	4200
15	10*	208		290						4	841	58	1.1	17.2*	5.3	320	5500
25	16*	357		190						4	1278	87	1.4	26.4*	9.5	408	8270
7	5*	104		650						4	434	30	17.5	9.2*	2.7	224	2800
7	5*	89		650						4	434	30	17.5	9.2*	2.7	224	2800
7	5*	89		650						4	434	30	17.5	9.2*	2.7	224	2800
11	8*	198		399						4	646	42	1.1	13.2*	4.3	278	4200
25	16*	357		190						4	1278	87	1.4	26.4*	9.5	408	8270
11	8*	39		399						4	646	42	1.1	13.2*	4.3	278	4200
15	10*	50		290						4	841	58	1.1	17.2*	5.3	320	5500
25	16*	50		190						4	1278	87	1.4	26.4*	9.5	408	8270
7	5*	25		650						4	434	30	17.5	9.2*	2.7	224	2800
7	5*	89		650						4	434	30	17.5	9.2*	2.7	19	2800
11	8*	198		399						4	646	42	1.1	13.2*	4.3	278	4200
15	10*	208		290						4	841	58	1.1	17.2*	5.6	320	5500
25	16*	357		190						4	1278	87	1.4	26.4*	9.5	408	8270
7	5*	104		650						4	434	30	1	9.2*	2.7	224	2800
11	8*	28		399						4	646	42	1.1	13.2*	4.3	278	4200
15	10*	28		290						4	841	58	1.1	17.2*	5.3	320	5500
25	16*	28		190						4	1278	87	1.4	26.4*	9.5	408	8270
7	5*	25		650						4	434	30	1	9.2*	2.7	224	2800

I _D (A)		P _D (W)		10V	R _{DS(ON)} (mΩ max) at V _{GS} =					VGS(th) (max V)	Ciss (pF)	Coss (pF)	Crss (pF)	Qg (nC)	Qgd (nC)	Trr (ns)	Qrr (nC)
25°C	70°C	25°C	70°C		4.5V	2.5V	1.8V	1.5V	1.2V								
20	12*	32		190						4.4	1935	55	1.25	34	8.7	265	3600

* For bottom exposed packages, the I_D and P_D are calculated at 100°C, otherwise at 70°C.

* R_{DS(ON)} measured at V_{GS} other than 10V, 4.5V, 1.8V, 1.5V, or 1.2V.

* Qg measured with V_{GS} = 10V. In all other cases V_{GS} = 4.5V.

Planar High Voltage MOSFETs

Part Number	Package	Configuration	Popular Application	Type	ESD Diode	Schottky Diode	Schottky Type	V _{DS} (V)	V _{GS} (±V)
V_{DS} = 500V									
AOB12N50	TO-263	Single	High Voltage	N	No	No		500	30
AOB14N50	TO-263	Single	High Voltage	N	No	No		500	30
AOD3N50	TO-252	Single	High Voltage	N	No	No		500	30
AOD5N50	TO-252	Single	High Voltage	N	No	No		500	30
AOD6N50	TO-252	Single	High Voltage	N	No	No		500	30
AOK22N50	TO-247	Single	High Voltage	N	No	No		500	30
AOT12N50	TO-220	Single	High Voltage	N	No	No		500	30
AOT13N50	TO-220	Single	High Voltage	N	No	No		500	30
AOT14N50	TO-220	Single	High Voltage	N	No	No		500	30
AOT14N50FD	TO-220	Single	High Voltage	N	No	No		500	30
AOT16N50	TO-220	Single	High Voltage	N	No	No		500	30
AOT22N50	TO-220	Single	High Voltage	N	No	No		500	30
AOT3N50	TO-220	Single	High Voltage	N	No	No		500	30
AOT5N50	TO-220	Single	High Voltage	N	No	No		500	30
AOT8N50	TO-220	Single	High Voltage	N	No	No		500	30
AOT9N50	TO-220	Single	High Voltage	N	No	No		500	30
AOTF10N50FD	TO-220F	Single	High Voltage	N	No	No		500	30
AOTF12N50	TO-220F	Single	High Voltage	N	No	No		500	30
AOTF12T50P	TO-220F	Single	High Voltage	N	No	No		500	30
AOTF12T50PL	TO-220F	Single	High Voltage	N	No	No		500	30
AOTF13N50	TO-220F	Single	High Voltage	N	No	No		500	30
AOTF14N50	TO-220F	Single	High Voltage	N	No	No		500	30
AOTF14N50FD	TO-220F	Single	High Voltage	N	No	No		500	30
AOTF16N50	TO-220F	Single	High Voltage	N	No	No		500	30
AOTF22N50	TO-220F	Single	High Voltage	N	No	No		500	30
AOTF3N50	TO-220F	Single	High Voltage	N	No	No		500	30
AOTF5N50	TO-220F	Single	High Voltage	N	No	No		500	30
AOTF5N50FD	TO-220F	Single	High Voltage	N	No	No		500	30
AOTF8N50	TO-220F	Single	High Voltage	N	No	No		500	30
AOTF8T50P	TO-220F	Single	High Voltage	N	No	No		500	30
AOTF9N50	TO-220F	Single	High Voltage	N	No	No		500	30
AOU3N50	TO-251	Single	High Voltage	N	No	No		500	30
AOW12N50	TO-262	Single	High Voltage	N	No	No		500	30
AOW14N50	TO-262	Single	High Voltage	N	No	No		500	30
AOWF12N50	TO-262F	Single	High Voltage	N	No	No		500	30
AOWF14N50	TO-262F	Single	High Voltage	N	No	No		500	30
AOWF8N50	TO-262F	Single	High Voltage	N	No	No		500	30

1. Not recommended for new designs. Please contact your local sales office for a replacement part, if any.
 2. On-resistance Static Source-Source, otherwise Static Drain-Source.

I _D (A)		P _D (W)		R _{DS(ON)} (mΩ max) at V _{GS} =						V _{GS(th)}	C _{iss}	C _{oss}	C _{rss}	Q _g	Q _{gd}	T _{rr}	Q _{rr}
25°C	70°C	25°C	70°C	10V	4.5V	2.5V	1.8V	1.5V	1.2V	(max V)	(pF)	(pF)	(pF)	(nC)	(nC)	(ns)	(nC)
12	8.4*	250		520						4.5	1361	167	12.6	30.7	13	231	2820
14	11*	278		380						4.5	1914	191	16	44	29	289	4930
2.8	1.8*	57		3000						4.7	276	31.4	2.6	6.7	2.7	134	890
5	3.1*	104		1600						4.5	538	58	4.5	11.5*	4.1	182	2200
5.3	3.3*	104		1400						4.5	538	58	4.5	11.5*	4.1	182	2200
22	15*	417		260						4.5	3086	290	24	69*	24	524	9600
12	8.4*	250		520						4.5	1361	167	12.6	29.1	20.1	231	2820
13	8.5*	250		510						4.5	1361	167	12.6	30.7*	13	302	4700
14	11*	278		380						4.5	1914	191	16	42.8*	20.3	289	4930
14	9.6*	278		470						4	1654	179	14.5	38.8*	17.5	90	300
16	11*	278		370						4.5	1914	191	16	42.8*	20.3	334	6000
22	15*	417		260						4.5	3086	290	24	69*	24	524	9600
3	1.9*	74		3000						4.5	276	31.4	2.6	6.7*	2.7	134	890
5	3.3*	104		1500						4.5	517	57	4.9	15.5*	7.2	166	1370
9	6*	176		850						4.5	868	93	7.8	23.6*	10.6	206	2100
9	6*	192		850						4.5	868	93	7.8	23.6*	10.6	248	3500
10	6*	50		750						4.2	1030	112	10	29*	9.5	116	300
12	8.4*	50		520						4.5	1361	167	12.6	29.1	20.1	231	2820
12	8*	43		500						5	1477	63	6.3	22*	5.5	428	6100
12	8*	33		500						5	1477	63	6.3	22*	5.5	428	6100
13	8.5*	50		510						4.5	1361	167	12.6	30.7*	13	302	4700
14	11*	50		380						4.5	1914	191	16	44	29	289	4930
14	9.6*	50		470						4	1654	179	14.5	38.8*	17.5	90	300
16	11*	50		370						4.5	1914	191	16	42.8*	20.3	334	6000
22	15*	50		260						4.5	3086	290	24	69*	24	524	9600
3	1.9*	31		3000						4.7	276	31.4	2.6	6.7	2.7	134	890
5	3.3*	35		1500						4.7	517	57	4.9	15.5	7.2	166	1370
5	3*	35		1800						4.2	440	50	4.5	11*	3.8	87	200
9	6*	38.5		850						4.6	868	93	7.8	23.6	10.6	206	2100
8	5.4*	38		810						5	905	42	3.5	13*	3.4	340	3500
9	6*	38.5		850						4.6	868	93	7.8	23.6*	10.6	248	3500
2.8	1.8*	57		3000						4.7	276	31.4	2.6	6.7*	2.7	134	890
12	8.4*	250		520						4.5	1361	167	12.6	30.7*	13	231	2820
14	11*	278		380						4.5	1914	191	16	42.8*	20.3	289	4930
12	8.4*	28		520						4.5	1361	167	12.6	30.7*	13	231	2820
14	11*	28		380						4.5	1914	191	16	42.8*	20.3	289	4930
8	6*	27.8		850						4.5	868	93	7.8	23.6*	10.6	206	2100

* For bottom exposed packages, the I_D and P_D are calculated at 100°C, otherwise at 70°C.

* R_{DS(ON)} measured at V_{GS} other than 10V, 4.5V, 1.8V, 1.5V, or 1.2V.

* Q_g measured with V_{GS} = 10V. In all other cases V_{GS} = 4.5V.

Planar High Voltage MOSFETs (Continued)

Part Number	Package	Configuration	Popular Application	Type	ESD Diode	Schottky Diode	Schottky Type	V _{DS} (V)	V _{GS} (±V)
V_{DS} = 600V									
AO3160	SOT23A	Single	High Voltage	N	No	No		600	20
AO3162	SOT23-3	Single	High Voltage	N	No	No		600	30
AOB10N60	TO-263	Single	High Voltage	N	No	No		600	30
AOB11N60	TO-263	Single	High Voltage	N	No	No		600	30
AOB12N60FD	TO-263	Single	High Voltage	N	No	No		600	30
AOD1N60	TO-252	Single	High Voltage	N	No	No		600	30
AOD2N60	TO-252	Single	High Voltage	N	No	No		600	30
AOD2N60A	TO-252	Single	High Voltage	N	No	No		600	30
AOD3N60	TO-252	Single	High Voltage	N	No	No		600	30
AOD4N60	TO-252	Single	High Voltage	N	No	No		600	30
AOD7N60	TO-252	Single	High Voltage	N	No	No		600	30
AOI1N60	TO-251A	Single	High Voltage	N	No	No		600	30
AOI2N60	TO-251A	Single	High Voltage	N	No	No		600	30
AOI2N60A	TO-251A	Single	High Voltage	N	No	No		600	30
AOI4N60	TO-251A	Single	High Voltage	N	No	No		600	30
AOI4T60	TO-251A	Single	High Voltage	N	No	No		600	30
AOI4T60P	TO-251A	Single	High Voltage	N	No	No		600	30
AOI7N60	TO-251A	Single	High Voltage	N	No	No		600	30
AOT10N60	TO-220	Single	High Voltage	N	No	No		600	30
AOT11N60	TO-220	Single	High Voltage	N	No	No		600	30
AOT12N60	TO-220	Single	High Voltage	N	No	No		600	30
AOT12N60FD	TO-220	Single	High Voltage	N	No	No		600	30
AOT1N60	TO-220	Single	High Voltage	N	No	No		600	30
AOT20N60	TO-220	Single	High Voltage	N	No	No		600	30
AOT2N60	TO-220	Single	High Voltage	N	No	No		600	30
AOT3N60	TO-220	Single	High Voltage	N	No	No		600	30
AOT4N60	TO-220	Single	High Voltage	N	No	No		600	30
AOT5N60	TO-220	Single	High Voltage	N	No	No		600	30
AOT7N60	TO-220	Single	High Voltage	N	No	No		600	30
AOT8N60	TO-220	Single	High Voltage	N	No	No		600	30
AOTF10N60	TO-220F	Single	High Voltage	N	No	No		600	30
AOTF11N60	TO-220F	Single	High Voltage	N	No	No		600	30
AOTF12N60	TO-220F	Single	High Voltage	N	No	No		600	30
AOTF12N60FD	TO-220F	Single	High Voltage	N	No	No		600	30
AOTF20N60	TO-220F	Single	High Voltage	N	No	No		600	30
AOTF2N60	TO-220F	Single	High Voltage	N	No	No		600	30
AOTF4N60	TO-220F	Single	High Voltage	N	No	No		600	30
AOTF7N60	TO-220F	Single	High Voltage	N	No	No		600	30
AOTF7N60FD	TO-220F	Single	High Voltage	N	No	No		600	30
AOTF8N60	TO-220F	Single	High Voltage	N	No	No		600	30
AOTF11N62	TO-220F	Single	High Voltage	N	No	No		620	30
AOU1N60	TO-251	Single	High Voltage	N	No	No		600	30
AOU2N60	TO-251	Single	High Voltage	N	No	No		600	30
AOU2N60A	TO-251	Single	High Voltage	N	No	No		600	30

1. Not recommended for new designs. Please contact your local sales office for a replacement part, if any.
2. On-resistance Static Source-Source, otherwise Static Drain-Source.

I _D (A)		P _D (W)		R _{DS(ON)} (mΩ max) at V _{GS} =						VGS(th)	Ciss	Coss	Crss	Qg	Qgd	Trr	Qrr
25°C	70°C	25°C	70°C	10V	4.5V	2.5V	1.8V	1.5V	1.2V	(max V)	(pF)	(pF)	(pF)	(nC)	(nC)	(ns)	(nC)
0.04	0.03	1.39	0.89	500000	600000					3.2	10	1.8	0.7	1*	0.52	105	9.5
0.034	0.028	1.39	0.89	500000						4.1	4.2	0.45	0.05	0.7*	0.05	105	9.5
10	7.2*	250		750						4.5	1320	130	9.3	31	14.4	290	3900
11	8*	272		700						4.5	1656	146	11.2	30.6*	9.6	500	5900
12	8*	278		650						4	1659	166	15.8	41*	19	135	500
1.3	0.8*	45		9000						5	130	14.5	1.8	6.1	3.1	114	630
2	1.4*	56.8		4400						5	270	29	2.8	9.5	4.7	154	800
2	1.4*	57		4700						4.5	295	30	2.3	6.5*	1.8	268	1600
2.5	1.6*	56.8		3500						5	304	31.4	3.3	9.9	4.6	175	1400
4	2.6*	104		2300						4.5	528	53	4.8	12*	4.4	190	2400
7	4.5*	178		1300						4.5	975	88	7.3	19.3*	6.9	388	4400
1.3	0.8*	45		9000						4.5	130	14.5	1.8	6.1	3.1	114	630
2	1.4*	56.8		4400						4.5	270	29	2.8	9.5*	4.7	154	800
2	1.4*	57		4700						4.5	295	30	2.3	6.5*	1.8	268	1600
4	2.6*	104		2300						4.5	528	53	4.8	12*	4.4	190	2400
4	2.5*	83		2100						5	460	22	3.5	9*	2.4	384	3900
4	2.5*	83		2100						5	460	22	3.5	9*	2.4	384	3900
7	4.5*	178		1300						4.5	975	88	7.3	19.3*	6.9	388	4400
10	7.2*	250		750						4.5	1320	130	9.3	31.1	14.4	290	3900
11	8*	272		650						4.5	1656	146	11.2	30.6*	9.6	500	5900
12	9.7*	278		550						4.5	1751	164	13	40*	17.9	311	5200
12	8*	278		650						4	1659	166	15.8	41*	19	135	500
1.3	0.9*	41.7		9000						4.5	130	14.5	1.8	6.1	3.1	114	630
20	12*	417		370						4.5	3061	273	22.8	61*	24	480	10500
2	1.7*	74		4400						5	270	29	2.8	9.5	4.7	154	800
2.5	1.9*	59.5		3500						5	304	31.4	3.3	9.9	4.6	175	1400
4	2.7*	104		2200						4.5	511	51	4.4	15	7.6	212	1600
5	3.4*	132		1800						4.5	583	58.4	5.3	16.8	8.5	208	2000
7	4.8*	192		1200						4.5	861	84	6.6	23	11.2	255	2600
8	6.2*	208		900						4.5	1140	109	7.8	28.4	13.4	270	3300
10	7.2*	60		750						5	1320	130	9.3	31.1	14.4	290	3900
11	8*	50		650						4.5	1656	146	11.2	30.6*	9.6	500	5900
12	9.7*	50		550						4.5	1751	164	13	40*	17.9	311	5200
12	8*	50		650						4	1659	166	15.8	41*	19	135	500
20	12*	50		370						4.5	3061	273	22.8	61*	24	480	10500
2	1.7*	31		4400						5	270	29	2.8	9.5	4.7	154	800
4	2.7*	35		2200						4.5	511	51	4.4	15	7.6	212	1600
7	4.8*	38.5		1200						4.5	861	84	6.6	23.2	11.2	255	2600
7	4.7*	39		1450						4.2	826	86	7.9	20*	7.7	76	300
8	6.2*	50		900						4.5	1140	109	7.8	28.4	13.4	270	3300
11	8*	50		650						4.5	1656	146	11.2	30.6*	9.6	500	5900
1.3	0.8*	45		9000						5	130	14.5	1.8	6.1	3.1	114	630
2	1.4*	56.8		4400						5	270	29	2.8	9.5	4.7	154	800
2	1.4*	57		4700						4.5	295	30	2.3	6.5*	1.8	288	1600

* For bottom exposed packages, the I_D and P_D are calculated at 100°C, otherwise at 70°C.

* R_{DS(ON)} measured at V_{GS} other than 10V, 4.5V, 1.8V, 1.5V, or 1.2V.

* Qg measured with V_{GS} = 10V. In all other cases V_{GS} = 4.5V.

Planar High Voltage MOSFETs (Continued)

Part Number	Package	Configuration	Popular Application	Type	ESD Diode	Schottky Diode	Schottky Type	V _{DS} (V)	V _{GS} (±V)
AOU3N60	TO-251	Single	High Voltage	N	No	No		600	30
AOU4N60	TO-251	Single	High Voltage	N	No	No		600	30
AOW10N60	TO-262	Single	High Voltage	N	No	No		600	30
AOW11N60	TO-262	Single	High Voltage	N	No	No		600	30
AOW12N60	TO-262	Single	High Voltage	N	No	No		600	30
AOWF10N60	TO-262F	Single	High Voltage	N	No	No		600	30
AOWF11N60	TO-262F	Single	High Voltage	N	No	No		600	30
AOWF12N60	TO-262F	Single	High Voltage	N	No	No		600	30
AOWF4N60	TO-262F	Single	High Voltage	N	No	No		600	30
V_{DS} = 650V									
AOB12N65L	TO-263	Single	High Voltage	N	No	No		650	30
AOD7N65	TO-252	Single	High Voltage	N	No	No		650	30
AOI7N65	TO-251A	Single	High Voltage	N	No	No		650	30
AOK18N65	TO-247	Single	High Voltage	N	No	No		650	30
AOT10N65	TO-220	Single	High Voltage	N	No	No		650	30
AOT12N65	TO-220	Single	High Voltage	N	No	No		650	30
AOT7N65	TO-220	Single	High Voltage	N	No	No		650	30
AOT8N65	TO-220	Single	High Voltage	N	No	No		650	30
AOTF10N65	TO-220F	Single	High Voltage	N	No	No		650	30
AOTF12N65	TO-220F	Single	High Voltage	N	No	No		650	30
AOTF18N65	TO-220F	Single	High Voltage	N	No	No		650	30
AOTF7N65	TO-220F	Single	High Voltage	N	No	No		650	30
AOTF8N65	TO-220F	Single	High Voltage	N	No	No		650	30
AOW10N65	TO-262	Single	High Voltage	N	No	No		650	30
AOW12N65	TO-262	Single	High Voltage	N	No	No		650	30
AOWF10N65	TO-262F	Single	High Voltage	N	No	No		650	30
AOWF12N65	TO-262F	Single	High Voltage	N	No	No		650	30

1. Not recommended for new designs. Please contact your local sales office for a replacement part, if any.
 2. On-resistance Static Source-Source, otherwise Static Drain-Source.

I _D (A)		P _D (W)		R _{DS(ON)} (mΩ max) at V _{GS} =						V _{GS(th)}	C _{iss}	C _{oss}	C _{rss}	Q _g	Q _{gd}	T _{rr}	Q _{rr}
25°C	70°C	25°C	70°C	10V	4.5V	2.5V	1.8V	1.5V	1.2V	(max V)	(pF)	(pF)	(pF)	(nC)	(nC)	(ns)	(nC)
2.5	1.6*	56.8		3500						5	304	31.4	3.3	9.9	4.6	175	1400
4	2.6*	104		2300						4.5	528	53	4.8	12*	4.4	190	2400
10	7.2*	250		750						4.5	1320	130	9.3	31*	14.4	290	3900
11	8*	272		700						4.5	1656	146	11.2	30.6*	9.6	500	5900
12	9.7*	278		550						4.5	1751	164	13	40*	17.9	311	5200
10	7.2*	28		750						4.5	1320	130	9.3	31*	14.4	290	3900
11	8*	27.8		650						4.5	1656	146	11.2	30.6*	9.6	500	5900
12	9.7*	28		550						4.5	1751	164	13	40*	17.9	311	5200
4	2.6*	25		2300						4.5	528	53	4.8	12*	4.4	190	2400
12	7.7*	278		720						4.5	1792	152	11.5	39.8	16.8	375	7500
7	4.3*	178		1560						4.5	982	86	7	19.6*	8.2	365	4300
7	4.3*	178		1560						4.5	982	86	7	19.6*	8.2	365	4300
18	12*	417		390						4.5	3027	271	22	56*	19.6	655	10000
10	6.2*	250		1000						4.5	1369	118	10	27.7*	11.3	320	6000
12	7.7*	278		720						4.5	1792	152	11.5	39.8*	16.8	375	7500
7	4.4*	192		1500						4.5	887	77	7	19*	8.3	280	4200
8	5.2*	208		1150						4.5	1165	101	9	23.5*	9.5	295	5000
10	6.2*	50		1000						5	1369	118	10	27.7*	11.3	320	6000
12	7.7*	50		720						5	1792	152	11.5	39.8*	16.8	375	7500
18	12*	50		390						4.5	3027	271	22	56*	19.6	655	10000
7	4.4*	38.5		1560						5	887	77	7	19*	8.3	280	4200
8	5.2*	50		1150						5	1165	101	9	23.5*	9.5	295	5000
10	6.2*	250		1000						4.5	1369	118	10	27.7*	11.3	320	6000
12	7.7*	278		720						4.5	1792	152	11.5	39.8*	16.8	375	7500
10	6.2*	28		1000						4.5	1369	118	10	27.7*	11.3	320	6000
12	7.7*	28		720						4.5	1792	152	11.5	39.8*	16.8	375	7500

* For bottom exposed packages, the I_D and P_D are calculated at 100°C, otherwise at 70°C.

* R_{DS(ON)} measured at V_{GS} other than 10V, 4.5V, 1.8V, 1.5V, or 1.2V.

* Q_g measured with V_{GS} = 10V. In all other cases V_{GS} = 4.5V.

Planar High Voltage MOSFETs (Continued)

Part Number	Package	Configuration	Popular Application	Type	ESD Diode	Schottky Diode	Schottky Type	V _{DS} (V)	V _{GS} (±V)
V_{DS} = 700V and over									
AOB9N70L	TO-263	Single	High Voltage	N	No	No		700	30
AOD3N80	TO-252	Single	High Voltage	N	No	No		800	30
AOD2N100	TO-252	Single	High Voltage	N	No	No		1000	30
AOK8N80	TO-247	Single	High Voltage	N	No	No		800	30
AOK10N90	TO-247	Single	High Voltage	N	No	No		900	30
AOK9N90	TO-247	Single	High Voltage	N	No	No		900	30
AOK5N100	TO-247	Single	High Voltage	N	No	No		1000	30
AOT11N70	TO-220	Single	High Voltage	N	No	No		700	30
AOT7N70	TO-220	Single	High Voltage	N	No	No		700	30
AOT9N70	TO-220	Single	High Voltage	N	No	No		700	30
AOT3N100	TO-220	Single	High Voltage	N	No	No		1000	30
AOT5N100	TO-220	Single	High Voltage	N	No	No		1000	30
AOTF11N70	TO-220F	Single	High Voltage	N	No	No		700	30
AOTF7N70	TO-220F	Single	High Voltage	N	No	No		700	30
AOTF9N70	TO-220F	Single	High Voltage	N	No	No		700	30
AOTF3N80	TO-220F	Single	High Voltage	N	No	No		800	30
AOTF8N80	TO-220F	Single	High Voltage	N	No	No		800	30
AOTF10N90	TO-220F	Single	High Voltage	N	No	No		900	30
AOTF3N90	TO-220F	Single	High Voltage	N	No	No		900	30
AOTF4N90	TO-220F	Single	High Voltage	N	No	No		900	30
AOTF6N90	TO-220F	Single	High Voltage	N	No	No		900	30
AOTF9N90	TO-220F	Single	High Voltage	N	No	No		900	30
AOTF3N100	TO-220F	Single	High Voltage	N	No	No		1000	30
AOTF5N100	TO-220F	Single	High Voltage	N	No	No		1000	30
AOWF11N70	TO-262F	Single	High Voltage	N	No	No		700	30
AOWF9N70	TO-262F	Single	High Voltage	N	No	No		700	30

1. Not recommended for new designs. Please contact your local sales office for a replacement part, if any.
 2. On-resistance Static Source-Source, otherwise Static Drain-Source.

I _D (A)		P _D (W)		R _{DS(ON)} (mΩ max) at V _{GS} =						VGS(th)	Ciss	Coss	Crss	Qg	Qgd	Trr	Qrr
25°C	70°C	25°C	70°C	10V	4.5V	2.5V	1.8V	1.5V	1.2V	(max V)	(pF)	(pF)	(pF)	(nC)	(nC)	(ns)	(nC)
9	5.8*	236		1200						4.5	1357	113	7.4	28.5*	11.6	375	7500
2.8	1.8*	83		4800						4.5	510	39	3.7	10*	2.9	344	2200
2	1.2*	83		9000						4.5	477	31	2.7	9.7*	3.5	287	2200
7.4	4.6*	50		1630						4.5	1375	101	11	26	9.1	484	6000
10	7*	403		980						4.5	2630	190	18	60*	27	575	9900
9	6*	368		1300						4.5	2130	152	14	46*	20.5	568	7800
4	2.5*	42		4200						4.5	950	62	6	19*	6.5	450	5500
11	7.2*	271		870						4.5	1793	146	10.5	37.5*	15	400	9000
7	4.2*	198		1800						4.5	978	80	7	20.5*	7.9	270	5900
9	5.8*	236		1200						4.5	1357	113	7.4	28.5*	11.6	375	7500
2.8	1.8*	132		6000						4.5	690	44	5	15	4.7	400	3700
4	2.5*	195		4200						4.5	950	62	6	19*	6.5	450	5500
11	7.2*	50		870						4.5	1793	146	10.5	37.5*	15	400	9000
7	4.2*	38.5		1800						4.5	978	80	7	20.5*	7.9	270	5900
9	5.8*	50		1200						4.5	1357	113	7.4	28.5*	11.6	375	7500
2.8	1.8*	35		4800						4.5	510	39	3.7	10*	2.9	344	2200
7.4	4.6*	50		1630						4.5	1375	101	11	26	9.1	484	6000
10	7*	50		980						4.5	2630	190	18	13*	27	575	9900
2.4	1.5*	35		6700						4.5	444	34	3.3	2.7*	4.1	655	7000
4	2.5*	37		3600						4.5	728	52	5.5	18.4*	8	196	4050
6	3.9*	50		2200						4.5	1196	82	7.8	29*	13	286	5600
9	6*	50		1300						4.5	2130	152	14	9.5*	20.5	586	7800
2.8	1.8*	38		6000						4.5	690	44	5	15	4.7	400	3700
4	2.5*	42		4200						4.5	950	62	6	19*	6.5	450	5500
11	7.2*	28		870						4.5	1793	146	10.5	37.5*	15	400	9000
9	5.8*	28		1200						4.5	1357	113	7.4	28.5*	11.6	375	7500

* For bottom exposed packages, the I_D and P_D are calculated at 100°C, otherwise at 70°C.

* R_{DS(ON)} measured at V_{GS} other than 10V, 4.5V, 1.8V, 1.5V, or 1.2V.

* Qg measured with V_{GS} = 10V. In all other cases V_{GS} = 4.5V.

Intelligent Power Modules (IPMs)

Part Number		Package	Description	Input Logic	Rated Voltage (V)	Rated Current (A)	Emitter Configuration
DIP							
AIM5C05B060N1	NEW	DIP-23	3-Phase IGBT IPM	Active High	600	5	Common
AIM5C10B060M3	NEW	DIP-23	3-Phase IGBT IPM	Active High	600	10	Common
AIM5D05B060N1	NEW	DIP-23	3-Phase IGBT IPM	Active High	600	5	Separated
AIM5D10B060M1	NEW	DIP-23	3-Phase IGBT IPM	Active High	600	10	Separated
AIM5D10B060M3	NEW	DIP-23	3-Phase IGBT IPM	Active High	600	10	Separated

Insulated-Gate Bipolar Transistors (IGBTs) – Single

Part Number	Package	Configuration	V_{CE} (max) (V)		I_C (max) (A)		$V_{CE(sat)}$ (typ) (V)	E_{ON} (typ) (mJ)	E_{OFF} (typ) (mJ)	Q_g (typ) (nC)
					25°C	100°C				
TO-220										
AOTS40B65H1	TO-220	IGBT	650		80	40	1.9	1.27	0.46	63
TO-247										
AOKS40B65H1	TO-247	IGBT	650		80	40	1.9	1.27	0.46	63
AOKS30B60D1	TO-247	IGBT	600		60	30	2	1.1	0.24	34
AOKS40B60D1	TO-247	IGBT	600		80	40	1.85	1.55	0.3	45

Insulated-Gate Bipolar Transistors (IGBTs) – Co-Pack

Part Number	Package	Configuration	V_{CE} (max) (V)		I_C (max) (A)	
					25°C	100°C
TO-220						
AOT5B65M1	TO-220	IGBT with Anti-Parallel Diode	650		10	5
AOT10B65M1	TO-220	IGBT with Anti-Parallel Diode	650		10	10
AOT10B65M2	TO-220	IGBT with Anti-Parallel Diode	650		10	10
AOT15B65M1	TO-220	IGBT with Anti-Parallel Diode	650		30	15
AOT20B65M1	TO-220	IGBT with Anti-Parallel Diode	650		40	20
AOT5B60D	TO-220	IGBT with Anti-Parallel Diode	600		10	5
AOT10B60D	TO-220	IGBT with Anti-Parallel Diode	600		20	10
AOT15B60D	TO-220	IGBT with Anti-Parallel Diode	600		30	15
TO-220F						
AOTF5B65M1	TO-220F	IGBT with Anti-Parallel Diode	650		10	5
AOTF5B65M2	TO-220F	IGBT with Anti-Parallel Diode	650		10	5
AOTF10B65M1	TO-220F	IGBT with Anti-Parallel Diode	650		20	10
AOTF10B65M2	TO-220F	IGBT with Anti-Parallel Diode	650		20	10
AOTF15B65M1	TO-220F	IGBT with Anti-Parallel Diode	650		30	15
AOTF15B65M2	TO-220F	IGBT with Anti-Parallel Diode	650		30	15
AOTF20B65M1	TO-220F	IGBT with Anti-Parallel Diode	650		40	20
AOTF20B65M2	TO-220F	IGBT with Anti-Parallel Diode	650		40	20
AOTF5B60D	TO-220F	IGBT with Anti-Parallel Diode	600		10	5
AOTF10B60D	TO-220F	IGBT with Anti-Parallel Diode	600		20	10
AOTF10B60D2	TO-220F	IGBT with Anti-Parallel Diode	600		23	10
AOTF15B60D	TO-220F	IGBT with Anti-Parallel Diode	600		30	15
AOTF15B60D2	TO-220F	IGBT with Anti-Parallel Diode	600		23	15

$V_{CE(sat)}$ (typ) (V)	E_{ON} (typ) (mJ)	E_{OFF} (typ) (mJ)	Q_g (typ) (nC)	V_F (typ) (V)	Q_{rr} (typ) (μ C)	I_{rm} (typ) (A)
1.57	0.08	0.07	14	1.8	0.24	2.78
1.6	0.18	0.13	24	1.9	0.4	3.8
1.6	0.18	0.13	24	1.6	0.45	4
1.7	0.29	0.2	32	1.77	0.7	4.7
1.7	0.47	0.27	46	1.66	0.8	5.2
1.55	0.14	0.04	9.4	1.46	0.23	4.4
1.53	0.26	0.07	17.4	1.52	0.25	5
1.6	0.42	0.11	25.4	1.43	0.48	5.8
1.57	0.08	0.07	14	1.8	0.24	2.78
1.57	0.08	0.07	14	1.48	0.27	3.5
1.6	0.18	0.13	24	1.9	0.4	3.8
1.6	0.18	0.13	24	1.6	0.5	4
1.7	0.29	0.2	32	1.77	0.7	4.7
1.7	0.29	0.2	32	1.5	0.7	5.4
1.7	0.47	0.27	46	1.66	0.8	5.2
1.7	0.58	0.28	46	1.56	0.8	5.6
1.55	0.14	0.04	9.4	1.46	0.23	4.4
1.53	0.26	0.07	17.4	1.52	0.25	5
1.55	0.14	0.04	9.4	1.46	0.23	4.4
1.6	0.42	0.11	25.4	1.43	0.48	5.8
1.53	0.26	0.07	17.4	1.52	0.25	5


Insulated-Gate Bipolar Transistors (IGBTs) – Co-Pack (Continued)

Part Number	Package	Configuration	V _{CE} (max) (V)	I _C (max) (A)		
				25°C	100°C	
TO-247						
AOK20B135D1	TO-247	IGBT with Anti-Parallel Diode	1350	40	20	
AOK20B135E1	TO-247	IGBT with Anti-Parallel Diode	1350	40	20	
AOK30B135W1	TO-247	IGBT with Anti-Parallel Diode	1350	60	30	
AOK20B120E1	TO-247	IGBT with Anti-Parallel Diode	1200	40	20	
AOK20B120E2	TO-247	IGBT with Anti-Parallel Diode	1200	40	20	
AOK20B120D1	TO-247	IGBT with Anti-Parallel Diode	1200	40	20	
AOK30B120D2	TO-247	IGBT with Anti-Parallel Diode	1200	60	30	
AOK40B120H1	NEW	TO-247	IGBT with Anti-Parallel Diode	1200	80	40
AOK40B120M1	TO-247	IGBT with Anti-Parallel Diode	1200	80	40	
AOK20B65M1	TO-247	IGBT with Anti-Parallel Diode	650	40	20	
AOK20B65M2	TO-247	IGBT with Anti-Parallel Diode	650	40	20	
AOK30B65M2	TO-247	IGBT with Anti-Parallel Diode	650	60	30	
AOK40B65H1	TO-247	IGBT with Anti-Parallel Diode	650	80	40	
AOK40B65H2AL	TO-247	IGBT with Anti-Parallel Diode	650	80	40	
AOK40B65M3	TO-247	IGBT with Anti-Parallel Diode	650	80	40	
AOK50B65H1	TO-247	IGBT with Anti-Parallel Diode	650	100	50	
AOK50B65M2	TO-247	IGBT with Anti-Parallel Diode	650	80	40	
AOK60B65H1	TO-247	IGBT with Anti-Parallel Diode	650	120	60	
AOK60B65M3	TO-247	IGBT with Anti-Parallel Diode	650	120	60	
AOK75B65H1	TO-247	IGBT with Anti-Parallel Diode	650	150	75	
AOK10B60D	TO-247	IGBT with Anti-Parallel Diode	600	20	10	
AOK15B60D	TO-247	IGBT with Anti-Parallel Diode	600	30	15	
AOK20B60D1	TO-247	IGBT with Anti-Parallel Diode	600	40	20	
AOK30B60D	TO-247	IGBT with Anti-Parallel Diode	600	60	30	
AOK30B60D1	TO-247	IGBT with Anti-Parallel Diode	600	60	30	
AOK40B60D	TO-247	IGBT with Anti-Parallel Diode	600	80	40	
AOK40B60D1	TO-247	IGBT with Anti-Parallel Diode	600	80	40	
AOK50B60D1	TO-247	IGBT with Anti-Parallel Diode	600	100	50	
AOK60B60D1	TO-247	IGBT with Anti-Parallel Diode	600	120	60	
AOK75B60D1	TO-247	IGBT with Anti-Parallel Diode	600	150	75	
TO-252						
AOD5B65M1	TO-252	IGBT with Anti-Parallel Diode	650	10	5	
AOD5B65M1H	NEW	TO-252	IGBT with Anti-Parallel Diode	650	10	5
AOD5B65N1	TO-252	IGBT with Anti-Parallel Diode	650	10	5	
AOD5B60D	TO-252	IGBT with Anti-Parallel Diode	600	10	5	
AOD7B65M3	TO-252	IGBT with Anti-Parallel Diode	650	14	7	
TO-263						
AOB5B65M1	TO-263	IGBT with Anti-Parallel Diode	650	10	5	
AOB10B65M1	TO-263	IGBT with Anti-Parallel Diode	650	20	10	
AOB15B65M1	TO-263	IGBT with Anti-Parallel Diode	650	30	15	
AOB5B60D	TO-263	IGBT with Anti-Parallel Diode	600	10	5	
AOB10B60D	TO-263	IGBT with Anti-Parallel Diode	600	20	10	
AOB15B60D	TO-263	IGBT with Anti-Parallel Diode	600	30	15	
AOB20B65M1	TO-263	IGBT with Anti-Parallel Diode	650	40	20	

$V_{CE(sat)}$ (typ) (V)	E_{ON} (typ) (mJ)	E_{OFF} (typ) (mJ)	Q_g (typ) (nC)	V_F (typ) (V)	Q_{rr} (typ) (μ C)	I_{rm} (typ) (A)
1.57		1.05	66	1.46		
1.8		0.8	58	1.6		
1.8		1.47	62	1.6		
1.68		0.83	60.5	1.6		
1.75		0.82	53.5	1.6		
1.54		0.94	67.5	1.33		
1.77		1.28	67	1.5		
1.8	2.45	1.24	128	2.8	1.1	6.5
1.95	3.87	1.25	140	2.5	1.5	9.3
1.7	0.47	0.27	46	1.66	1.6	7.1
1.7	0.58	0.28	46	1.56	0.8	5.6
1.66	1.02	0.41	63	1.56	1.2	7.4
1.9	1.27	0.46	63	2.22	1	6.2
2.05	1.17	0.54	61	2.12	0.7	4.7
1.95	1.3	0.5	59	2.22	1	6
1.9	1.92	0.85	76	2.25	0.9	6.3
1.95	1.3	0.5	59	2.22	1	6
1.88	2.42	1.17	90	2.08	1.2	7.8
1.94	2.6	1.3	106	1.91	1.3	7.5
1.85	3.77	2.04	109	2.15	1.2	7.9
1.53	0.32	0.07	17.4	1.52	0.25	5
1.6	0.51	0.11	25.4	1.43	0.48	5.8
1.85	0.76	0.18	24.6	1.35	0.43	6.5
1.6	1.18	0.2	47	1.34	0.8	9.5
1.85	1.1	0.24	34	1.47	0.50	7
1.6	1.72	0.3	63.5	1.36	0.86	10
1.85	1.55	0.3	45	1.42	0.63	8
1.85	2.37	0.5	64	1.4	0.77	9
1.85	3.1	0.73	75	1.34	0.84	10
1.72	3.7	1.3	118	1.44	0.9	10
1.57	0.08	0.07	14	1.8	0.24	2.78
1.57	0.08	0.07	14	1.8	0.24	2.78
2.5	0.081	0.049	9.2	2.13	0.19	2.5
1.6	0.14	0.04	9.4	1.46	0.23	4.4
1.87	0.108	0.099	14	2.6	0.29	3
1.57	0.08	0.07	14	1.8	0.24	2.78
1.6	0.18	0.13	24	1.9	0.4	3.8
1.7	0.29	0.2	32	1.77	0.7	4.7
1.55	0.18	0.09	9.4	1.46	0.23	4.4
1.6	0.26	0.07	17.4	1.52	0.25	5
1.6	0.42	0.11	25.4	1.43	0.48	5.8
1.7	0.47	0.27	46	1.66	0.8	5.2


PACKAGE TYPE

AOS delivers advanced package technologies that meet the ever-increasing performance and power-efficiency requirements of our customers. We offer a range of package options to support a wide spectrum of end-applications, from



NOTE: Images are not to scale

handheld, to computing, to consumer, and high-power industrial applications.



NOTE: Images are not to scale

LEFT BLANK INTENTIONALLY

AOS SALES OFFICES

UNITED STATES

475 Oakmead Parkway
Sunnyvale, CA 94085
Phone: +1 (408) 830-9742
Fax: +1 (408) 830-9749
Email: Inquiries@aosmd.com

EUROPE

Phone: + 44 7785 575089
Email: Ewilliams@aosmd.com

HONG KONG

Room 701, Tesbury Center
28 Queen's Road East
Wanchai
Phone: +86 (755) 8351-7733
Email: AOSChina@aosmd.com

TAIWAN

9/F, No. 292 Yangguang Street
Neihu District
Taipei City 11491
Phone: +886 (2) 8751-5616
Fax: +886 (2) 2627-4762
Email: AOSTaiwan@aosmd.com

CHINA

Shenzhen

East 10/F, Matsunichi Building
#9996 Shennan Blvd.
Shenzhen 518057
Phone: +86 (755) 8351-7733
Fax: +86 (755) 835-15883
Email: AOSChina@aosmd.com

Shanghai

Room 1002-1005, Tower 1,
Kerry EverBright City
218 Tianmu West Road
Shanghai 200070
Phone: +86 (21) 6353-3218
Fax: +86 (21) 6353-9339
Email: AOSChina@aosmd.com

Beijing

Phone: +86 (186) 1126-3304
Email: Qsbi@aosmd.com

Chengdu

Phone: +86 (180) 1112-2993
Email: Zhongwu@aosmd.com

Qingdao

Phone: +86 (180) 0532-0539
Email: Yszhang@aosmd.com

JAPAN

10F, Koujimachi Sunrise Building
Koujimachi 2-2-31, Chiyoda-ku
Tokyo 102-0083
Phone: +81 (3) 5211-5822
Fax: +81 (3) 5211-5823
Email: AOSJapan@aosmd.com

SOUTH KOREA

10th Floor, Bandi Building
Bongeunsa-ro 114
Gangnam-gu
Seoul 135-907
Phone: +82 (2) 557-8501
Fax: +82 (2) 557-8420
Email: AOSKorea@aosmd.com

ASEAN

Email: AOSasean@aosmd.com

To contact any of our sales partners
worldwide, please visit our website
at: www.aosmd.com/contact

