

Final datasheet

EasyPACK™ 1B module with CoolMOS™ CFD7A Automotive MOSFET and PressFIT / NTC

Features

- Electrical features
 - $V_{DSS} = 650\text{ V}$
 - $I_{DN} = 35\text{ A} / I_{DRM} = 70\text{ A}$
 - Low switching losses
 - Low inductive design
 - Integrated snubber
- Mechanical features
 - PressFIT contact technology
 - Integrated NTC temperature sensor
 - Rugged mounting due to integrated mounting clamps



Typical appearance

Potential applications

- Automotive auxillary applications
- DC charger for EV
- High-frequency switching application

Product validation

- Qualified according to AQC 324, release no.: 02.1/2019

Description




Table of contents

	Description	1
	Features	1
	Potential applications	1
	Product validation	1
	Table of contents	2
1	Package	3
2	MOSFET	3
3	Body diode (MOSFET)	5
4	Capacitor	5
5	NTC-Thermistor	6
6	Characteristics diagrams	7
7	Circuit diagram	12
8	Package outlines	13
9	Module label code	14
	Revision history	15
	Disclaimer	16

1 Package

Table 1 Insulation coordination

Parameter	Symbol	Note or test condition	Values	Unit
Isolation test voltage	V_{ISOL}	RMS, $f = 50$ Hz, $t = 1$ min	2.5	kV
Internal isolation		basic insulation (class 1, IEC 61140)	Al_2O_3	
Creepage distance	d_{Creep}	terminal to heatsink	11.5	mm
Creepage distance	d_{Creep}	terminal to terminal	6.3	mm
Clearance	d_{Clear}	terminal to heatsink	10.0	mm
Clearance	d_{Clear}	terminal to terminal	4.2	mm
Comparative tracking index	CTI		> 200	
Relative thermal index (electrical)	RTI	housing	140	°C

Table 2 Characteristic values

Parameter	Symbol	Note or test condition	Values			Unit
			Min.	Typ.	Max.	
Module lead resistance, terminals - chip	$R_{CC'+EE'}$	$T_H = 25$ °C, per switch		3.3		mΩ
Storage temperature	T_{stg}		-40		125	°C
Mounting force per clamp	F		20		50	N
Weight	G			24		g

Note: The current under continuous operation is limited to 25 A rms per connector pin.

2 MOSFET

Table 3 Maximum rated values

Parameter	Symbol	Note or test condition	Values	Unit	
Drain-source voltage	V_{DSS}		$T_{vj} = 25$ °C	650	V
			$T_{vj} = -40$ °C	605	
Implemented drain current	I_{DN}		35	A	
Continuous DC drain current	I_{DDC}	$T_{vj} = 150$ °C, $V_{GS} = 10$ V	$T_H = 65$ °C	30	A
Repetitive peak drain current	I_{DRM}	verified by design, t_p limited by T_{vjmax}	70	A	
Gate-source voltage, max. transient voltage	V_{GS}	$f_{repetition} \leq 100$ kHz, $t_{pulse} \leq 2$ ns	±30	V	

(table continues...)

Table 3 (continued) Maximum rated values

Parameter	Symbol	Note or test condition	Values	Unit
Gate-source voltage, max. static voltage	V_{GS}		±20	V
dv/dt ruggedness	dv/dt	$V_{DS} = 0 \dots 400$ V	120	V/ns

Table 4 Characteristic values

Parameter	Symbol	Note or test condition	Values			Unit	
			Min.	Typ.	Max.		
Drain-source on-resistance	$R_{DS(on)}$	$I_D = 35$ A	$V_{GS} = 10$ V, $T_{vj} = 25$ °C		30	39.4	mΩ
			$V_{GS} = 10$ V, $T_{vj} = 125$ °C		53		
			$V_{GS} = 10$ V, $T_{vj} = 150$ °C		61		
Gate threshold voltage	$V_{GS(th)}$	$I_D = 1.74$ mA, $V_{DS} = V_{GS}$, $T_{vj} = 25$ °C	3.55	4	4.45	V	
Total gate charge	Q_G	$V_{DD} = 400$ V, $V_{GS} = 10$ V		0.141		μC	
Internal gate resistor	R_{Gint}	$T_{vj} = 25$ °C		3.8		Ω	
Input capacitance	C_{ISS}	$f = 100$ kHz, $V_{DS} = 400$ V, $V_{GS} = 0$ V		6.95		nF	
Output capacitance	C_{OSS}	$f = 100$ kHz, $V_{DS} = 400$ V, $V_{GS} = 0$ V		0.092		nF	
Reverse transfer capacitance	C_{rSS}	$f = 100$ kHz, $V_{DS} = 400$ V, $V_{GS} = 0$ V		0.021		nF	
C_{OSS} stored energy	E_{OSS}	$V_{DS} = 400$ V, $V_{GS} = 10$ V, $T_{vj} = 25$ °C		17.9		μJ	
Drain-source leakage current	I_{DSS}	$V_{DS} = 650$ V, $V_{GS} = 0$ V			10	μA	
Gate-source leakage current	I_{GSS}	$V_{DS} = 0$ V, $T_{vj} = 25$ °C	$V_{GS} = 20$ V		100	nA	
Turn-on delay time (inductive load)	$t_{d on}$	$I_D = 35$ A, $R_{Gon} = 12$ Ω, $V_{DD} = 400$ V, $V_{GS} = 0/10$ V	$T_{vj} = 25$ °C		146		ns
			$T_{vj} = 125$ °C		145		
			$T_{vj} = 150$ °C		145		
Rise time (inductive load)	t_r	$I_D = 35$ A, $R_{Gon} = 12$ Ω, $V_{DD} = 400$ V, $V_{GS} = 0/10$ V	$T_{vj} = 25$ °C		11.5		ns
			$T_{vj} = 125$ °C		12.4		
			$T_{vj} = 150$ °C		12.8		
Turn-off delay time (inductive load)	$t_{d off}$	$I_D = 35$ A, $R_{Goff} = 0$ Ω, $V_{DD} = 400$ V, $V_{GS} = 0/10$ V	$T_{vj} = 25$ °C		106		ns
			$T_{vj} = 125$ °C		114		
			$T_{vj} = 150$ °C		117		

(table continues...)

Table 4 (continued) Characteristic values

Parameter	Symbol	Note or test condition	Values			Unit	
			Min.	Typ.	Max.		
Fall time (inductive load)	t_f	$I_D = 35\text{ A}$, $R_{\text{Goff}} = 0\ \Omega$, $V_{\text{DD}} = 400\text{ V}$, $V_{\text{GS}} = 0/10\text{ V}$	$T_{\text{vj}} = 25\text{ }^\circ\text{C}$		4.7		ns
			$T_{\text{vj}} = 125\text{ }^\circ\text{C}$		5.6		
			$T_{\text{vj}} = 150\text{ }^\circ\text{C}$		5.9		
Thermal resistance, junction to heat sink	R_{thJH}	per MOSFET, $\lambda_{\text{grease}} = 1\text{ W}/(\text{m}\cdot\text{K})$		0.992		K/W	
Temperature under switching conditions	$T_{\text{vj op}}$		-40		150	$^\circ\text{C}$	

3 Body diode (MOSFET)

Table 5 Maximum rated values

Parameter	Symbol	Note or test condition	Values	Unit
DC body diode forward current	I_{SD}	$T_{\text{vj}} = 25\text{ }^\circ\text{C}$, $V_{\text{GS}} = 0\text{ V}$	$T_{\text{H}} = 65\text{ }^\circ\text{C}$ 35	A
dv/dt ruggedness	dv/dt	$V_{\text{DS}} = 0\dots 400\text{ V}$, $I_{\text{SD}} \leq 35\text{ A}$	$T_{\text{vj}} = 25\text{ }^\circ\text{C}$ 70	V/ns
di/dt ruggedness	di/dt	$V_{\text{DS}} = 0\dots 400\text{ V}$, $I_{\text{SD}} \leq 35\text{ A}$	$T_{\text{vj}} = 25\text{ }^\circ\text{C}$ 1300	A/ μs

Table 6 Characteristic values

Parameter	Symbol	Note or test condition	Values			Unit	
			Min.	Typ.	Max.		
Forward voltage	V_{SD}	$I_{\text{SD}} = 35\text{ A}$, $V_{\text{GS}} = 0\text{ V}$	$T_{\text{vj}} = 25\text{ }^\circ\text{C}$		1.05	1.35	V
			$T_{\text{vj}} = 125\text{ }^\circ\text{C}$		0.92		
			$T_{\text{vj}} = 150\text{ }^\circ\text{C}$		0.88		

4 Capacitor

Table 7 Characteristic values

Parameter	Symbol	Note or test condition	Values			Unit
			Min.	Typ.	Max.	
Rated DC voltage	V_{DC}	$T = 25\text{ }^\circ\text{C}$		630		V
Capacitance value	C_{nom}	$T = 25\text{ }^\circ\text{C}$		66		nF
Temperature range	T_{cap}		-40		125	$^\circ\text{C}$

5 NTC-Thermistor

Table 8 Characteristic values


Parameter	Symbol	Note or test condition	Values			Unit
			Min.	Typ.	Max.	
Rated resistance	R_{25}	$T_{NTC} = 25\text{ °C}$	9.7	10	10.3	kΩ
Power dissipation	P_{25}	$T_{NTC} = 25\text{ °C}$			20	mW
B-value	$B_{25/50}$	$R_2 = R_{25} \exp[B_{25/50}(1/T_2 - 1/(298,15\text{ K}))]$		3447		K
B-value	$B_{25/80}$	$R_2 = R_{25} \exp[B_{25/80}(1/T_2 - 1/(298,15\text{ K}))]$		3487		K
B-value	$B_{25/100}$	$R_2 = R_{25} \exp[B_{25/100}(1/T_2 - 1/(298,15\text{ K}))]$		3510		K

Note: For an analytical description of the NTC characteristics please refer to AN2009-10, chapter 4

6 Characteristics diagrams


Output characteristic (typical), MOSFET

$I_D = f(V_{DS})$
 $V_{GS} = 10\text{ V}$




Output characteristic field (typical), MOSFET

$I_D = f(V_{DS})$
 $T_{vj} = 25^\circ\text{C}$




Output characteristic field (typical), MOSFET

$I_D = f(V_{DS})$
 $T_{vj} = 150^\circ\text{C}$



Drain source on-resistance (typical), MOSFET


$R_{DS(on)} = f(I_D)$
 $V_{GS} = 10\text{ V}$



6 Characteristics diagrams


Drain source on-resistance (typical), MOSFET

$R_{DS(on)} = f(T_{vj})$
 $I_D = 35\text{ A}$




Transfer characteristic (typical), MOSFET

$I_D = f(V_{GS})$
 $V_{DS} = 20\text{ V}$




Gate-source threshold voltage (typical), MOSFET

$V_{GS(th)} = f(T_{vj})$
 $V_{GS} = V_{DS}$



Gate charge characteristic (typical), MOSFET

$V_{GS} = f(Q_G)$
 $I_D = 35\text{ A}, T_{vj} = 25\text{ °C}$




6 Characteristics diagrams

Capacity characteristic (typical), MOSFET

$C = f(V_{DS})$


$T_{vj} = 25\text{ °C}$, $f = 100\text{ kHz}$, $V_{GS} = 0\text{ V}$



Switching times (typical), MOSFET

$t = f(I_D)$


$R_{Goff} = 0\text{ }\Omega$, $R_{Gon} = 12\text{ }\Omega$, $V_{DD} = 400\text{ V}$, $T_{vj} = 150\text{ °C}$, $V_{GS} = 0/10\text{ V}$



Switching times (typical), MOSFET

$t = f(R_G)$


$V_{DD} = 400\text{ V}$, $I_D = 35\text{ A}$, $T_{vj} = 150\text{ °C}$, $V_{GS} = 0/10\text{ V}$



Voltage slope (typical), MOSFET

$dv/dt = f(R_G)$

$V_{DD} = 400\text{ V}$, $I_D = 35\text{ A}$, $V_{GS} = 0/10\text{ V}$




6 Characteristics diagrams

Reverse bias safe operating area (RBSOA), MOSFET


$I_D = f(V_{DS})$

$R_{Goff} = 0 \Omega$, $T_{vj} = 150 \text{ }^\circ\text{C}$, $V_{GS} = 0/10 \text{ V}$



Transient thermal impedance, MOSFET


$Z_{th} = f(t)$



Forward characteristic body diode (typical), MOSFET

$I_{SD} = f(V_{SD})$


$T_{vj} = 25 \text{ }^\circ\text{C}$



Forward characteristic body diode (typical), MOSFET

$I_{SD} = f(V_{SD})$


$T_{vj} = 150 \text{ }^\circ\text{C}$



Forward voltage of body diode (typical), MOSFET


$V_{SD} = f(T_{vj})$

$I_{SD} = 35 \text{ A}$



Temperature characteristic (typical), NTC-Thermistor

$R = f(T_{NTC})$



7 Circuit diagram




Figure 1

8 Package outlines




Figure 2

9 Module label code

Module label code			
Code format	Data Matrix	Barcode Code128	
Encoding	ASCII text	Code Set A	
Symbol size	16x16	23 digits	
Standard	IEC24720 and IEC16022	IEC8859-1	
Code content	<i>Content</i> Module serial number Module material number Production order number Date code (production year) Date code (production week)	<i>Digit</i> 1 - 5 6 - 11 12 - 19 20 - 21 22 - 23	<i>Example</i> 71549 142846 55054991 15 30
Example	 		<p>71549142846550549911530</p> <p>71549142846550549911530</p>

Figure 3

Revision history

Revision history

Document revision	Date of release	Description of changes
0.10	2022-03-17	Initial version
0.20	2022-06-20	Preliminary datasheet
1.00	2022-06-21	Final datasheet
1.10	2023-08-22	10424AERRA

Trademarks

All referenced product or service names and trademarks are the property of their respective owners.

Edition 2023-08-22

Published by

Infineon Technologies AG

81726 Munich, Germany

© 2023 Infineon Technologies AG

All Rights Reserved.

Do you have a question about any aspect of this document?

Email: erratum@infineon.com

Document reference

IFX-ABC458-004

Important notice

The information given in this document shall in no event be regarded as a guarantee of conditions or characteristics ("Beschaffheitsgarantie").

With respect to any examples, hints or any typical values stated herein and/or any information regarding the application of the product, Infineon Technologies hereby disclaims any and all warranties and liabilities of any kind, including without limitation warranties of non-infringement of intellectual property rights of any third party.

In addition, any information given in this document is subject to customer's compliance with its obligations stated in this document and any applicable legal requirements, norms and standards concerning customer's products and any use of the product of Infineon Technologies in customer's applications.

The data contained in this document is exclusively intended for technically trained staff. It is the responsibility of customer's technical departments to evaluate the suitability of the product for the intended application and the completeness of the product information given in this document with respect to such application.

Warnings

Due to technical requirements products may contain dangerous substances. For information on the types in question please contact your nearest Infineon Technologies office.

Except as otherwise explicitly approved by Infineon Technologies in a written document signed by authorized representatives of Infineon Technologies, Infineon Technologies' products may not be used in any applications where a failure of the product or any consequences of the use thereof can reasonably be expected to result in personal injury.