Harvatek Surface Mount LED Data Sheet T1341MND-20P000712U1930

7						
Official Product	HT Part No. T1341MND-20P000712U1930					
Tentative Product	*******					
Specifications are subject to changes for improvement without advance notice. Proprietary data, drawings, company confidential all rights reserved.		06/20/2022	Version 1.2	Page 1/16		

DISCLAIMER
LIFE SUPPORT POLICY
PRODUCT SPECIFICATIONS
ATTENTION: ELECTROSTATIC DISCHARGE (ESD) PROTECTION4
LABEL SPECIFICATIONS
SPECIFICATIONS RANGE
PRODUCT FEATURES
ELECTRO-OPTICAL CHARACTERISTICS8
PACKAGE OUTLINE DIMENSION AND RECOMMENDED SOLDERING PATTERN FOR REFLOW
Soldering
ABSOLUTE MAXIMUM RATINGS8
CHARACTERISTICS OF T1341MND9
PRECAUTION FOR USE10
PACKAGING11
TAPE DIMENSION
REEL DIMENSION
Packing
Dry Раск
BAKING
Precautions
HANDLING OF SILICONE RESIN LEDS14
REFLOW SOLDERING15
Reworking15
CLEANING
CAUTIONS OF PICK AND PLACE16
REVISE HISTORY16

7							
Official Product	HT Part No. T1341MND-20P000712U1930						
Tentative Product	******						
Specifications are subject to changes for improvement without advance notice. Proprietary data, drawings, company confidential all rights reserved.		06/20/2022	Version 1.2	Page 2/16			

DISCLAIMER

HARVATEK reserves the right to make changes without further notice to any products herein to improve reliability, function or design. HARVATEK does not assume any liability arising out of the application or use of any product or circuit described herein; neither does it convey any license under its patent rights, nor the rights of others.

Life Support Policy

HARVATEK's products are not authorized for use as critical components in life support devices or systems without the express written approval of the President of HARVATEK or HARVATEK INTERNATIONAL. As used herein:

1. Life support devices or systems are devices or systems which, (a) are intended for surgical implant into the body, or (b) support or sustain life, and (c) whose failure to perform when properly used in accordance with instructions for use provided in the labeling, can be reasonably expected to result in a significant injury of the user.

2. A critical component in any component of a life support device or system whose failure to perform can be reasonably expected to cause the failure of the life support device or system, or to affect its safety or effectiveness.

7						
Official Product	HT Part No. T1341MND-20P000712U1930					
Tentative Product	*******					
Specifications are subject to changes for improvement without advance notice. Proprietary data, drawings, company confidential all rights reserved.		06/20/2022	Version 1.2	Page 3/16		

Product Specifications

Item	Specification	Material	Quantity
1) /	Min 7.68 lm		
IV	@20mA / T_s= 25 $^\circ\!\mathrm{C}$;Tolerance:±10%		
Chromaticity	As page 6-7		
Coordinate	@20mA/ $T_S\!\!=\!25^\circ\!\!\mathbb{C};\!Tolerance:\pm\!0.005$		
Vf	2.8-3.3V		
	@20mA/ T_s= 25 $^\circ\!\mathrm{C}$;Tolerance: ±0.05V		
lr	< 10 µA @ V _R = 5 V		
Resin	Yellow	Silicone Resin	
CRI	CRI>80, Tolerance <u>+</u> 2		
Carrier tape	EIA 481-1A specs	Conductive black tape	2000pcs per reel
Reel	EIA 481-1A specs	Conductive black	
Label	HT standard	Paper	
Packing bag	250x230mm	Aluminum laminated bag/ no-zipper	One reel per bag
Carton	HT standard	Paper	Non-specified

Others:

Each immediate box consists of 5 reels. The 5 reels may not necessarily have the same lot number or the same bin combinations of Iv, CIE and Vf. Each reel has a label identifying its specification; the immediate box consists of a product label as well.

Note : This is shipped test conditions

%Remarks: This product should be operated in forward bias. If a reverse voltage is continuously applied to the product, such operation can cause migration resulting in LED damage.

ATTENTION: Electrostatic Discharge (ESD) protection



The symbol to the left denotes that ESD precaution is needed. ESD protection for GaP and AlGaAs based chips is necessary even though they are relatively safe in the presence of low static-electric discharge. Parts built with AlGaInP, GaN, or/and InGaN based chips are **STATIC SENSITIVE devices**. ESD precaution must


be taken during design and assembly.

If manual work or processing is needed, please ensure the device is adequately protected from ESD during the process.

Official Product	HT Part No. T1341MND-20P000712U1930					
Tentative Product	*****					
Specifications are subject to changes for improvement without advance notice. Proprietary data, drawings, company confidential all rights reserved.		06/20/2022	Version 1.2	Page 4/16		

2. Qty

Label Specifications



Harvatek P/N:

Т	134	1	MND -	20P-	0007	12
Product	Package	Dice Qty	Color	Current	Series Number	Taping
LF	3.0(L)x1.4(W)x0.7(H) mm	1:Single	MND:White ,	20mA	X001~XZZZ	1.Taping style

CRI>80

Lot No.:

1	2	3	4	5	6	7	8	9	10
E	1	Α	1	Α	2	2	L	1	2
Cod	e 1 2	Code 3	Code 4	Code 5	Code 6	Code 7	Code 8	Code 9	Code 10
		Mfg. Year	Mfg. Month	Mfg. Date	Consecuti	ve number		Special code	9
Internal Tra	acing Code	2020-L 2021-M 2022-P 2023-Q 2026-T 2027-V 2030-Y 2031-Z 	1:Jan. 2:Feb. A:Oct. B:Nov. C:Dec.	1:A 2:B 3:C 26:Z 27:7 28:8 29:9 30:3 31:4	01-	-ZZ		000~ZZZ	

Official Product HT Part No. T1341MND-20P000712U1930						
Tentative Product	*************					
Specifications are subject to changes for improvement without advance notice. Proprietary data, drawings, company confidential all rights reserved.		06/20/2022	Version 1.2	Page 5/16		

Specifications Range

Iv) Bin:

Color	Bin Code	Spec. Range
MND	JD2	7.68~8.20 lm
	KA1	8.20~8.76 lm
	KB1	8.76~9.37 lm
	KC2	9.37~10.00 lm

Note: It maintains a tolerance of ±10% on IV


Color Bin:

Color	Bin Code	Х	Y	Bin Code	Х	Y
		0.3068	0.3113		0.3222	0.3243
		0.3048	0.3207		0.3215	0.3350
	CA	0.3130	0.3290	DA	0.3290	0.3417
		0.3144	0.3186		0.3290	0.3300
		0.3068	0.3113		0.3222	0.3243
		0.3144	0.3186		0.3215	0.3350
		0.3130	0.3290		0.3207	0.3462
	СВ	0.3213	0.3373	DC	0.3290	0.3538
		0.3221	0.3261		0.3290	0.3417
MND		0.3144	0.3186		0.3215	0.3350
IVIND		0.3048	0.3207			
		0.3028	0.3304			
	СС	0.3115	0.3391			
		0.3130	0.3290			
		0.3048	0.3207			
		0.3130	0.3290			
		0.3115	0.3391			
	CD	0.3205	0.3481			
		0.3213	0.3373			
		0.3130	0.3290			

Note: It maintains a tolerance of $x,y \pm 0.005$

7						
Official Product	HT Part No. T1341MND-20P000712U1930					
Tentative Product	*****	******				
Specifications are subject to changes for improvement without advance notice. Proprietary data, drawings, company confidential all rights reserved.		06/20/2022	Version 1.2	Page 6/16		

Chromaticity Coordinate



Forward Voltage (Vf) Bin:

Color	Bin Code	Spec. Range
	H1	2.8-2.9V
	H2	2.9-3.0V
MND	H3	3.0-3.1V
	H4	3.1-3.2V
	J1	3.2-3.3V


Note: It maintains a tolerance of ±0.05V on forward voltage measurements

7				
Official Product	HT Part No. T1341MND-20P000712U1930			
Tentative Product	*****	****		
	t to changes for improvement without advance awings, company confidential all rights reserved.	06/20/2022	Version 1.2	Page 7/16

Product Features

Electro-Optic	Electro-Optical Characteristics						
	T _{Soldering} , 25 °C)						
Series	Emitting Color	Motorial	VF	(V)	Chromaticity Coordinate	l _∨ (Lm)	Viewing Angle
Selles	Emitting Color	Material	typ	max	x,y	Typical	$2\theta \frac{1}{2}$
T1341MND-20	Cold White	InGaN	3.1	3.3	6300K	8.3	110

Package Outline Dimension and Recommended Soldering Pattern for Reflow Soldering



Absolute Maximum Ratings


					(T _{Soldering} 25 °C)
Series	P _D (mW)	I _F (mA)	I _{FP} (mA)*	T _{OP} (°C)	T _{ST} (°C)
Color	Power Dissipation	Forward Current	Pulse Forward Current	Operating Temperature	Storage Temperature
MND	105	30	80	-40~+85	-40~+100

 * Condition for I_{FP} is pulse of 1/10 duty and 0.1msec width

Official Product	HT Part No. T1341MND-20P000712U1930			
Tentative Product	*****	****		
	t to changes for improvement without advance awings, company confidential all rights reserved.	06/20/2022	Version 1.2	Page 8/16

Unit: mm Tolerance: +/-0.1

Characteristics of T1341MND




Official Product	HT Part No. T1341MND-20P000712U1930			
Tentative Product	*****	****		
	t to changes for improvement without advance awings, company confidential all rights reserved.	06/20/2022	Version 1.2	Page 9/16

Precaution for Use


- 1. The chips should not be used directly in any type of fluid such as water, oil, organic solvent, etc.
- 2. When the LEDs are illuminating, the maximum ambient temperature should be first considered before operation.
- 3. LEDs must be stored in a clean environment. A sealed container with a nitrogen atmosphere is necessary if the storage period is over 3 months after shipping.
- 4. The LEDs must be used within 4 weeks after unpacked. Unused products must be repacked in an anti-electrostatic package, folded to close any opening and then stored in a dry and cool space.
- 5. The appearance and specifications of the products may be modified for improvement without further notice.
- 6. The LEDs are sensitive to the static electricity and surge. It is strongly recommended to use a grounded wrist band and anti-electrostatic glove when handling the LEDs.If a voltage over the absolute maximum rating is applied to LEDs, it will damage LEDs.Damaged LEDs will show some abnormal characteristics such as remarkable increase of leak current, lower turn-on voltage and getting unlit at low current.

7				
Official Product	HT Part No. T1341MND-20P000712U1930			
Tentative Product	*****	****		
	t to changes for improvement without advance awings, company confidential all rights reserved.	06/20/2022	Version 1.2	Page 10/16

Packaging Tape Dimension




Dim. A	Dim. B	Dim. C	Qty/Reel
3.2 <u>+</u> 0.1	1.55±0.1	0.95±0.1	2K



Official Product	HT Part No. T1341MND-20P000712U1930			
Tentative Product	*****	****		
	t to changes for improvement without advance awings, company confidential all rights reserved.	06/20/2022	Version 1.2	Page 11/16

Reel Dimension



5 or 10 boxes per carton is available depending on shipment quantity.


Official Product	HT Part No. T1341MND-20P000712U1930			
Tentative Product	*****	****		
	t to changes for improvement without advance awings, company confidential all rights reserved.	06/20/2022	Version 1.2	Page 12/16

Dry Pack

All SMD optical devices are **MOISTURE SENSITIVE**. Avoid exposure to moisture at all times during transportation or storage. Every reel is packaged in a moisture protected anti-static bag. Each bag is properly sealed prior to shipment.

A humidity indicator will be included in the moisture protected anti-static bag prior to shipment.

The packaging sequence is as follows:



Baking

Baking before soldering is recommended when the package has been unsealed for 4 weeks. The conditions are as followings:

- 1. $60\pm3^{\circ}C\times(12\sim24hrs)$ and <5% RH, taped reel type.
- 2. 100±3°C ×(45min~1hr), bulk type.
- 3. 130±3°C ×(15min~30min), bulk type.

Precautions

- 1. Avoid exposure to moisture at all times during transportation or storage.
- 2. Anti-Static precaution must be taken when handling GaN, InGaN, and AlGaInP products.
- 3. It is suggested to connect the unit with a current limiting resistor of the proper size. Avoid applying a reverse voltage beyond the specified limit.
- 4. Avoid operation beyond the limits as specified by the absolute maximum ratings.
- 5. Avoid direct contact with the surface through which the LED emits light.
- 6. If possible, assemble the unit in a clean room or dust-free environment.

Official Product	HT Part No. T1341MND-20P000712U1930			
Tentative Product	*****	****		
	t to changes for improvement without advance awings, company confidential all rights reserved.	06/20/2022	Version 1.2	Page 13/16

Handling of Silicone Resin LEDs

Handling Indications

During processing, mechanical stress on the surface should be minimized as much as possible.

Sharp objects of all types should not be used to pierce the sealing compound.



Figure 1

In general, LEDs should only be handled from the side. By the way ,this also applies to LEDs without a silicone sealant, since the surface can also become scratched.




Figure 2

When populating boards in SMT production, there are basically no restrictions regarding the from of the pick and place nozzle, except that mechanical pressure on the surface of the resin must be prevented.

This is assured by choosing a pick and place nozzle which is large than LEDs reflector area.


Official Product	HT Part No. T1341MND-20P000712U1930			
Tentative Product	*****	****		
	t to changes for improvement without advance awings, company confidential all rights reserved.	06/20/2022	Version 1.2	Page 14/16

Reflow Soldering

Recommend soldering paste specifications:

- 1. Operating temp.: Above 217 ^oC ,60-150 sec.
- 2. Peak temp.:260 ^OCMax.,10sec Max.
- 3. Reflow soldering should not be done more than two times.
- 4. Never attempt next process until the component is cooled down to room temperature after reflow.
- 5. The recommended reflow soldering profile (measured on the surface of the LED terminal) is as following:

Lead-free Solder Profile



Reworking

- Rework should be completed within 5 seconds under 260 °C.
- The iron tip must not come in contact with the copper foil.
- Twin-head type is preferred.

Cleaning

Following are cleaning procedures after soldering:

- An alcohol-based solvent such as isopropyl alcohol (IPA) is recommended.
- Temperature x Time should be 50°C x 30sec. or <30°C x 3min

Official Product	HT Part No. T1341MND-20P000712U1930				
Tentative Product	*****	******			
Specifications are subject to changes for improvement without advance notice. Proprietary data, drawings, company confidential all rights reserved.		06/20/2022	Version 1.2	Page 15/16	

- Ultrasonic cleaning: < 15W/ bath; bath volume ≤ 1liter
- Curing: 100 ^OC max, <3min

Cautions of Pick and Place

- Avoid stress on the resin at elevated temperature.
- Avoid rubbing or scraping the resin by any object.
- Electric-static may cause damage to the component. Please ensure that the equipment is properly grounded. Use of an ionizer fan is recommended.

Revise History

Rev.	Descriptions	Date	Page
1.0			
1.1	Add Customer Product Code and Renew Form (Preliminary)	07/08/2021	P5
1.2	Add Customer Product Code and Renew Form	06/20/2022	-

7				
Official Product	HT Part No. T1341MND-20P000712U1930			
Tentative Product	*****	****		
Specifications are subject to changes for improvement without advance notice. Proprietary data, drawings, company confidential all rights reserved.		06/20/2022	Version 1.2	Page 16/16