

# Harvatek Surface Mount Reflective Interrupter Data Sheet T4642PTIRM3B000351U1930

Official Product	HT Part No. T4642PTIRM3B000351U1930	Customer Part No.	Data Sheet No.	
Tentative Product ************************************		******	-	
Specifications are subject to changes for improvement without advance notice. Proprietary data, drawings, company confidential all rights reserved.		11/25/2022	1.3	Page 1/17



DISCLAIMER	3
LIFE SUPPORT POLICY	3
PRODUCT SPECIFICATIONS	4
ATTENTION: ELECTROSTATIC DISCHARGE (ESD) PROTECTION	4
LABEL SPECIFICATIONS	5
ELECTRO-OPTICAL CHARACTERISTICS	7
PACKAGE OUTLINE DIMENSION AND RECOMMENDED SOLDERING PATTERN FOR REFLOW	
Soldering	9
CHARACTERISTICS OF T4642PTIR	
PACKAGING	13
TAPE DIMENSION	13
REEL DIMENSION	14
PACKING	14
DRY PACK	15
Baking	15
PRECAUTIONS	15
REFLOW SOLDERING	16
Reworking	16
CLEANING	16
CAUTIONS OF PICK AND PLACE	17
REVISE HISTORY	17

Official Product	HT Part No. T4642PTIRM3B000351U1930	Customer Part No.	Data Sheet No.	
Tentative Product	*******	******		-
Specifications are subject to changes for improvement without advance notice. Proprietary data, drawings, company confidential all rights reserved.		11/25/2022	1.3	Page 2/17



#### **DISCLAIMER**

HARVATEK reserves the right to make changes without further notice to any products herein to improve reliability, function or design. HARVATEK does not assume any liability arising out of the application or use of any product or circuit described herein; neither does it convey any license under its patent rights, nor the rights of others.

# **Life Support Policy**

HARVATEK's products are not authorized for use as critical components in life support devices or systems without the express written approval of the President of HARVATEK or HARVATEK INTERNATIONAL. As used herein:

- 1. Life support devices or systems are devices or systems which, (a) are intended for surgical implant into the body, or (b) support or sustain life, and (c) whose failure to perform when properly used in accordance with instructions for use provided in the labeling, can be reasonably expected to result in a significant injury of the user.
- 2. A critical component in any component of a life support device or system whose failure to perform can be reasonably expected to cause the failure of the life support device or system, or to affect its safety or effectiveness.

Official Product	HT Part No. T4642PTIRM3B000351U1930	Customer Part No.	Data She	et No.
Tentative Product	re Product ************************************		-	
Specifications are subject to changes for improvement without advance notice. Proprietary data, drawings, company confidential all rights reserved.		11/25/2022	1.3	Page 3/17



# **Product Specifications**

Item	Specification	Material	Quantity
Detector Spectral Bandwidth	700nm~1100nm		
$\lambda_{D}$	@ V <sub>CE</sub> =5V / T <sub>S</sub> = 25°C		
	Tolerance: ±10%		
Emitter Peak Wavelength	Typ: 940nm		
$\lambda_{P}$	@ 10 mA / $T_S = 25^{\circ}C$		
Collector Light Current	0.18~0.40 mA, Tolerance: ±10%		
Ic	@ V <sub>CE</sub> =5V , I <sub>F</sub> =10mA , d=1 mm		
Resin	Black	Silicone	
Carrier tape	EIA 481-1A specs	Conductive black tape	
Reel	EIA 481-1A specs	Conductive black	
Label	HT standard	Paper	
Packing bag	250x230mm	Aluminum laminated bag/ no-zipper	One reel per bag
Carton	HT standard	Paper	Non-specified

#### Others:

Each immediate box consists of 5 reels. The 5 reels may not necessarily have the same lot number or the same bin combinations of Iv, CIE and Vf. Each reel has a label identifying its specification; the immediate box consists of a product label as well.

Note: This is shipped test conditions

\*Remarks: This product should be operated in forward bias. If a reverse voltage is continuously applied to the product, such operation can cause migration resulting in LED damage.

#### ATTENTION: Electrostatic Discharge (ESD) protection



The symbol to the left denotes that ESD precaution is needed. ESD protection for GaP and AlGaAs based chips and Silicon semiconductor is necessary even though they are relatively safe in the presence of low static-electric discharge. Parts built with AlGaInP, GaN, or/and InGaN based chips are **STATIC SENSITIVE** 


devices. ESD precaution must be taken during design and assembly.

If manual work or processing is needed, please ensure the device is adequately protected from ESD during the process.

Official Product	HT Part No. T4642PTIRM3B000351U1930	Customer Part No.	Data Sheet No.	
Tentative Product	ative Product ************************************		-	
Specifications are subject to changes for improvement without advance notice. Proprietary data, drawings, company confidential all rights reserved.		11/25/2022	1.3	Page 4/17



# **Label Specifications**



## **■**Harvatek P/N:

T 464 2 PTIR M3B- 0003 51

Product	Package	Dice Q'ty	Туре	Voltage	Series Number	Taping
РСВ	4.6(L)x3.4(W)x1.62(H) mm	2:Bi	PT:Phototransistor	PT:5V	X001~XZZZ	1.Taping style
			IR:Infrared	IR:10mA		2. Q'ty

## ■ Lot No.:

1	2	3	4	5	6	7	8	9	10
E	1	Α	1	Α	2	2	L	1	2
Cod	e 1 2	Code 3	Code 4	Code 5	Code 6	Code 7	Code 8	Code 9	Code 10
		Mfg. Year	Mfg. Month	Mfg. Date	Consecuti	ve number		Special code	9
Internal Tra	acing Code	2020-L 2021-M 2022-P 2023-Q  2026-T 2027-V  2030-Y 2031-Z	1:Jan. 2:Feb.  A:Oct. B:Nov. C:Dec.	1:A 2:B 3:C  26:Z 27:7 28:8 29:9 30:3 31:4	01-	-ZZ		000-ZZZ	

Official Product	HT Part No. T4642PTIRM3B000351U1930	Customer Part No.	Data Sheet No.	
Tentative Product	*******	******	-	-
Specifications are subject to changes for improvement without advance notice. Proprietary data, drawings, company confidential all rights reserved.		11/25/2022	1.3	Page 5/17



# **Absolute Maximum Rating at 25℃**

Symbol	Parameters Ratings		Units	Notes				
INPUT (I	INPUT (Emitter)							
$V_R$	Reverse Voltage	5	V					
I <sub>F</sub>	Forward Current	50	mA					
I <sub>FP</sub>	Peak Forward Current	1	Α	1				
P <sub>d</sub>	Total Power Dissipation	75	mW					
OUTPUT	Γ (Detector)							
BV <sub>CEO</sub>	Collector-Emitter Breakdown Voltage	30	V	2				
BV <sub>ECO</sub>	Emitter-Collector Breakdown Voltage	5	V	3				
I <sub>C</sub>	Collector Current	20	mA					
P <sub>d</sub>	Total Power Dissipation	75	mW					
SENSOF	₹							
T <sub>opr</sub>	Operating Temperature	-40 ~ +85	$^{\circ}\!\mathbb{C}$					
T <sub>stg</sub>	Storage Temperature	-40 ~ +100	$^{\circ}\!\mathbb{C}$					
T <sub>sol</sub>	Soldering Temperature	260	$^{\circ}\!\mathbb{C}$	4				

## Notes:

1. I<sub>FP</sub> Conditions--Pulse Width≦100µs and Duty≦1%.

2. Test conditions :  $I_C=100\mu A$ ,  $E_e=0mW/cm^2$ .

3. Test conditions :  $I_E=100\mu A$ ,  $E_e=0mW/cm^2$ .

4. Soldering time  $\leq$  5 seconds.

Official Product	HT Part No. T4642PTIRM3B000351U1930	Customer Part No.	Data Sheet No.	
Tentative Product	********	******		-
Specifications are subject to changes for improvement without advance notice. Proprietary data, drawings, company confidential all rights reserved.		11/25/2022	1.3	Page 6/17



# **Electro-Optical Characteristics**

Symbol	Parameters	Test conditions	Min	Тур	Max	Units	Notes		
INPUT (Emitter)									
V <sub>F</sub>	Forward Voltage	I <sub>F</sub> =20mA	-	1.2	1.6	V			
λ <sub>P</sub>	Peak Wavelength	I <sub>F</sub> =10mA	-	940	-	nm			
I <sub>R</sub>	Reverse Current	V <sub>R</sub> =5V	-	-	10	μA			
OUTPUT	(Detector)	•			•				
V <sub>CE(sat)</sub>	Collector-Emitter Saturation Voltage	I <sub>C</sub> =2mA Ee=1mW/cm <sup>2</sup>	-	-	0.4	V			
I <sub>CEO</sub>	Collector Dark Current	V <sub>CE</sub> =10V Ee=0mW/cm <sup>2</sup>	-	-	100	nA			
SENSOR									
I <sub>C(ON)</sub>	Collector Light Current	V <sub>CE</sub> =5V I <sub>F</sub> =10mA d=1 mm	0.18	-	0.4	mA	5		
I <sub>LEAK</sub>	Leakage Current	$V_{CE}$ =5V $I_F$ =10mA with no reflection	-	-	1	μΑ			
t <sub>r</sub>	Rise Time	V <sub>CE</sub> =2V I <sub>C</sub> =100μA	-	20	-	μS			
t <sub>f</sub>	Fall Time	$R_L=1K\Omega$ $d=1 \text{ mm}$	-	20	-	μS	6		

## Notes:

5. Ic Bin Rank (mA):


Bin Code	ВХ3	BX4	BX5	BX6	BX7
Min	0.18	0.23	0.28	0.33	0.38
Max	0.23	0.28	0.33	0.38	0.4

Official Product	HT Part No. T4642PTIRM3B000351U1930	Customer Part No.	Data She	et No.
Tentative Product	********	******		-
	ct to changes for improvement without ry data, drawings, company confidential all	11/25/2022	1.3	Page 7/17




## Notes:

# 6. Test circuit:



# ■ Light Current Measurement Setup Diagram




Official Product	HT Part No. T4642PTIRM3B000351U1930	Customer Part No.	Data She	et No.
Tentative Product	********	******		-
	ct to changes for improvement without ry data, drawings, company confidential all	11/25/2022	1.3	Page 8/17



# Package Outline Dimension and Recommended Soldering Pattern for Reflow Soldering


(Unit: mm Tolerance: +/-0.1)





Official Product	HT Part No. T4642PTIRM3B000351U1930	Customer Part No.	Data She	et No.
Tentative Product	*******	******		-
	ct to changes for improvement without ry data, drawings, company confidential all	11/25/2022	1.3	Page 9/17




## Characteristics of T4642PTIR









Forward current , I<sub>F</sub> (mA)











Official Product	HT Part No. T4642PTIRM3B000351U1930	Customer Part No.	Data She	et No.
Tentative Product	********	******		-
	ct to changes for improvement without ry data, drawings, company confidential all	11/25/2022	1.3	Page 10/17











Official Product	HT Part No. T4642PTIRM3B000351U1930	Customer Part No.	Data She	et No.
Tentative Product	********	******		-
	ct to changes for improvement without ry data, drawings, company confidential all	11/25/2022	1.3	Page 11/17




#### **Precaution for Use**


- The chips should not be used directly in any type of fluid such as water, oil, organic solvent, etc.
- 2. When the LEDs are illuminating, the maximum ambient temperature should be first considered before operation.
- 3. LEDs must be stored in a clean environment. A sealed container with a nitrogen atmosphere is necessary if the storage period is over 3 months after shipping.
- 4. The LEDs must be used within 72 hours after unpacked. Unused products must be repacked in an anti-electrostatic package, folded to close any opening and then stored in a dry and cool space.
- 5. The appearance and specifications of the products may be modified for improvement without further notice.
- 6. The LEDs are sensitive to the static electricity and surge. It is strongly recommended to use a grounded wrist band and anti-electrostatic glove when handling the LEDs.If a voltage over the absolute maximum rating is applied to LEDs, it will damage LEDs.Damaged LEDs will show some abnormal characteristics such as remarkable increase of leak current, lower turn-on voltage and getting unlit at low current.

Official Product	HT Part No. T4642PTIRM3B000351U1930	Customer Part No.	Data She	et No.
Tentative Product	*******	******		-
	ct to changes for improvement without ry data, drawings, company confidential all	11/25/2022	1.3	Page 12/17




# Packaging Tape Dimension





Dim. A	Dim. B	Dim. C	Q'ty/Reel
4.95±0.10	3.60±0.10	1.72±0.10	1K


Unit: mm




Official Product	HT Part No. T4642PTIRM3B000351U1930	Customer Part No.	Data She	et No.
Tentative Product	*******	******		-
	ct to changes for improvement without ry data, drawings, company confidential all	11/25/2022	1.3	Page 13/17



## **Reel Dimension**



# **Packing**



5 or 10 boxes per carton is available depending on shipment quantity.

Official Product	HT Part No. T4642PTIRM3B000351U1930	Customer Part No.	Data She	et No.
Tentative Product	********	******	,	-
	ct to changes for improvement without ry data, drawings, company confidential all	11/25/2022	1.3	Page 14/17




# **Dry Pack**

All SMD optical devices are **MOISTURE SENSITIVE**. Avoid exposure to moisture at all times during transportation or storage. Every reel is packaged in a moisture protected anti-static bag. Each bag is properly sealed prior to shipment.

A humidity indicator will be included in the moisture protected anti-static bag prior to shipment.

The packaging sequence is as follows:



## **Baking**

Baking before soldering is recommended when the package has been unsealed for 72 hours. The conditions are as followings:

- 1.  $60\pm3^{\circ}$  ×(12~24hrs)and<5%RH, taped reel type.
- 2.  $100\pm3^{\circ}$ C × (45min~1hr), bulk type.
- 3.  $130\pm3^{\circ}$ C ×(15min~30min), bulk type.

# **Precautions**

- 1. Avoid exposure to moisture at all times during transportation or storage.
- 2. Anti-Static precaution must be taken when handling GaN, InGaN, and AlGaInP products.
- 3. It is suggested to connect the unit with a current limiting resistor of the proper size. Avoid applying a reverse voltage beyond the specified limit.
- 4. Avoid operation beyond the limits as specified by the absolute maximum ratings.
- 5. Avoid direct contact with the surface through which the LED emits light.
- 6. If possible, assemble the unit in a clean room or dust-free environment.

Official Product	HT Part No. T4642PTIRM3B000351U1930	Customer Part No.	Data She	et No.
Tentative Product	*******	******	,	-
	ct to changes for improvement without ry data, drawings, company confidential all	11/25/2022	1.3	Page 15/17




## **Reflow Soldering**

Recommend soldering paste specifications:

- 1. Operating temp.: Above 217°C ,60~150 sec
- 2. Peak temp.:260°C Max.,10sec Max.
- 3. Reflow soldering should not be done more than two times.
- Never take next process until the component is cooled down to room temperature after reflow.
- 5. The recommended reflow soldering profile (measuring on the surface of the LED terminal) is following:

Lead-free Solder Profile



## Reworking

- Rework should be completed within 5 seconds under 260°C.
- The iron tip must not come in contact with the copper foil.
- Twin-head type is preferred.

## Cleaning

Following are cleaning procedures after soldering:

- An alcohol-based solvent such as isopropyl alcohol (IPA) is recommended.
- Temperature x Time should be 50°C x 30sec. or <30°C x 3min</li>
- Ultra sonic cleaning: < 15W/ bath; bath volume ≤ 1liter</li>
- Curing: 100<sup>o</sup>C max, <3min</li>

Official Product	HT Part No. T4642PTIRM3B000351U1930	Customer Part No.	Data She	et No.
Tentative Product	********	******		-
	ct to changes for improvement without ry data, drawings, company confidential all	11/25/2022	1.3	Page 16/17



## **Cautions of Pick and Place**

- Avoid stress on the resin at elevated temperature.
- · Avoid rubbing or scraping the resin by any object.
- Electric-static may cause damage to the component. Please ensure that the equipment is properly grounded. Use of an ionizer fan is recommended.

# **Revise History**

Rev.	Descriptions	Date	Page
1.0	-	09/02/2019	
	Add IR: Forward Voltage VS. Forward Current, Relative		
	Intensity VS. Forward Current, Forward Current VS, Ambient		
1.1	Temperature, and Directive Characteristics.	04/10/2020	10,11
	Add PT: Collector Current VS. E <sub>e</sub> , and Collector Current VS.		
	Collector-Emitter Voltage.		
1.2	Add Collector Light Current IC: Tolerance: ±10%	11/20/2020	4
1.3	New Lot No.&New Form of Harvatek P/N	11/25/2022	5

Official Product	HT Part No. T4642PTIRM3B000351U1930	Customer Part No.	Data Sheet No.	
Tentative Product	********	******		-
Specifications are subject to changes for improvement without advance notice. Proprietary data, drawings, company confidential all rights reserved.		11/25/2022	1.3	Page 17/17