



Specification

Part No. : **FMA103.A.AF.001**

Product Name : Hercules Response 2 in 1 GPS/Galileo & First Net

Permanent Mount Antenna

Features : GPS/GALILEO – Two Stage 28dB+ LNA

FirstNet Band 14 Coverage

Low Profile, IP69K Rated Enclosure

Heavy Duty, UV and Vandal Resistant PC Housing

Permanent / Screw Mounting

Cables: 3M RG174 / TGC200

Connector: SMA(M)

Dimensions: H: 29mm x Ø49mm

RoHS Compliant







1. Introduction

The Hercules Response FMA103 GPS/GALILEO & FirstNet Combination Antenna is a combination high performance GPS/GALILEO and an LTE antenna that includes coverage on the FirstNet, Band 14 frequency.

FirstNet also known as Band 14 or PS-LTE (Public Service LTE) is a dedicated communications tool for First Responders in the US. It is an isolated network for providing faster critical information and data-sharing between blue light service providers and their agencies. New FirstNet devices are being deployed to allow for the multitude of services and applications which will be using the network for the following mission critical applications:

- Computer-aided dispatch (vehicle location)
- EMS Electronic Patient Care Reporting
- Vehicle Mounted RMS/ Citations/ Scanners
- Video Streaming

This antenna demonstrates extremely high efficiency also ensuring longer Battery life for high RF power handsets.

This antenna demonstrates extremely high efficiency which helps increase battery life for high RF power handsets. It is an ideal solution for reliable asset tracking, remote monitoring and public safety.





The durable, UV repellent PC housing helps resist vandalism and direct attacks. At just 29mm in height and a diameter of 49 mm, the Hercules can be mounted on metal or non-metal structures as it has a metal ground-plane base internally.

Cables and connectors are fully customizable, contact you regional Taoglas Sales Office for more information.





2. Specification

ELECTRICAL CELLULAR								
Standard		AMPS	GSM	PCS	DCS	3G		
Band (MHz)		850	900	1900	1800	2100		
Frequency (MHz)		824-896	880-960	1850-199 0	1710-188 0	1920 -2170		
Return Loss (dB)								
	0.3	-6.5	-6.0	-7	-8	-5		
Cabla lawath	1.0	-9.5	-8	-17	-16	-15		
Cable length (meter)	2.0	-10	-9	-20	-21	-18		
(meter)	3.0	-13	-11	-21	-21	-19		
	5.0	-14	-14	-25	-25	-23		
Efficiency (%)								
	0.3	38	54	58	54	50		
Cable length	1.0	31	35	36	42	31		
(meter)	2.0	23	20	23	32	21		
(meter)	3.0	25	29	23	22	18		
	5.0	11	11.5	12	11	11		
Peak Gain	Peak Gain (dBi)							
	0.3	2.0	3.3	4.0	3.6	3.0		
Cable length	1.0	1.2	1.3	2	1.8	1.2		
(meter)	2.0	0.5	-0.35	0	1.5	-0.1		
(meter)	3.0	0.1	1.6	0.6	0.1	-0.9		
	5.0	-2.5	-2.4	-2.3	-3.0	-2.0		
Polarizati	Polarization		Linear					
Impedan	ce	50 Ohms						
Input Power		10 Watts max.						
VSWR		<3.5.0:1						





	ELECTRICAL GPS	G/GALILEO						
Frequency	1	575.42MHz ± 1.023MHz						
Impedance		50 ohm						
VSWR		2.0 Max						
GPS/GALILEO Patch Gain	2.0	dB Passive Gain @ Zenit	:h					
GPS/GALILLO PALCII Gaiii	-1.0dB	Gain @ 10 degrees elev	ation					
Axial ratio		3.0 dB max						
Polarization		RHCP						
		fo = 1575.42MHz						
Out Band Rejection		fo ± 30 MHz 5dB Min.						
out build hojection	fo ± 50 MHz 20dB Min.							
		fo ± 100 MHz 25dB Min.						
Input Voltage	Min:1.8V	Typ. 3.0V	Max: 5.5V					
Total Gain @ Zenith	25dBic	30dBic	32dBic					
Current Consumption	6mA	6mA 12mA						
Noise Figure	2.7dB	3.0dB	3.7dB					
	MECHANICAL							
Dimensions	He	Height 29mm x Diameter 49mm						
Casing		UV resistant PC						
Base and thread		Nickel plated steel						
Thread diameter		18mm						
Weather proof gasket	CR4305 foa	CR4305 foam with 3M9448B double-side adhesive						
Cable pull		8 Kgf						
Recommended Mounting Tork	que							
Max Mounting Torque		29.4N·m						
Weight		200g						
	ENVIRONMI							
Waterproof		IP-67 & IP-69K						
Corrosion	5% NaCl for 4	5% NaCl for 48hrs - Nickel plated steel base and thread						
Temperature Range		-40°C to +85°C						
Thermal Shock		100 cycles -40°C to +80°C						
Humidity		Non-condensing 65°C 95% RH						
Shock (drop test)		1m drop on concrete 6 axes						

^{*}Note: The return loss, efficiency and gain measurements in the above table, were taken for the antenna mounted on a 30x30 cm metal plate. For a specific case performance refers to the below plots.





3. Test Setup




Figure 1. FMA103 Antenna test set up in free space, 30x30 cm metal plate and 60x60 cm





4. Antenna Parameters

4.1 Return Loss




Figure 2. Return Loss of the FMA103 antenna in free space




Figure 3. Return Loss of the FMA103 antenna on 30*30cm metal plate








Figure 4. Return Loss of the FMA103 antenna on 60*60cm metal plate








Figure 5. Efficiency of the FMA103 antenna in free space




Figure 6. Efficiency of the FMA103 antenna on 30*30cm metal plate








Figure 7. Efficiency of the FMA103 antenna on 60*60cm metal plate.




Figure 8. Efficiency of the FMA103 antenna with 960~1700MHz





4.3 Peak Gain




Figure 9. Gain of the FMA103 antenna in free space




Figure 10. Gain of the FMA103 antenna on 30*30cm metal plate








Figure 11. Gain of the FMA103 antenna on 60*60cm metal plate




Figure 12. Gain of the FMA103 antenna from 960~1700MHz





4.4 Radiation pattern




Figure 13. Radiation pattern at 849 MHz, Figure 1 as reference (dB), with 2 m RG174 cable and free space




Figure 14. Radiation pattern at 915 MHz, Figure 1 as reference (dB), with 2 m RG174 cable and free space








Figure 15. Radiation pattern at 1805 MHz, Figure 1 as reference (dB), with 2 m RG174 cable and free space




Figure 16. Radiation pattern at 1910 MHz, Figure 1 as reference (dB), with 2 m RG174 cable and free space








Figure 17. Radiation pattern at 2110 MHz, Figure 1 as reference (dB), with 2 m RG174 cable and free space.




Figure 18. Radiation pattern at 849 MHz, Figure 1 as reference (dB), with 2 m RG174 cable and 30x30 cm metal plate








Figure 19. Radiation pattern at 915 MHz, Figure 1 as reference (dB), with 2 m RG174 cable and 30x30 cm metal plate




Figure 20. Radiation pattern at 1805 MHz, Figure 1 as reference (dB), with 2 m RG174 cable and 30x30 cm metal plate








Figure 21. Radiation pattern at 1910 MHz, Figure 1 as reference (dB), with 2 m RG174 cable and 30x30 cm metal plate




Figure 22. Radiation pattern at 2110 MHz, Figure 1 as reference (dB), with 2 m RG174 cable and 30x30 cm metal plate








Figure 23. Radiation pattern at 849 MHz, Figure 1 as reference (dB), with 2 m RG174 cable and 60x60 cm metal plate




Figure 24. Radiation pattern at 915 MHz, Figure 1 as reference (dB), with 2 m RG174 cable and 60x60 cm metal plate








Figure 25. Radiation pattern at 1805 MHz, Figure 1 as reference (dB), with 2 m RG174 cable and 60x60 cm metal plate




Figure 26. Radiation pattern at 1910 MHz, Figure 1 as reference (dB), with 2 m RG174 cable and 60x60 cm metal plate









Figure 27. Radiation pattern at 2110 MHz, Figure 1 as reference (dB), with 2 m RG174 cable and 60x60 cm metal plate


5. System Block Diagram







6. GPS/GALILEO Patch Radiation Pattern




O degree is the top of Hercules.





7. LNA Properties

7.1 LNA Gain and Out-band Rejection @ 3.0V




(Cg1	Tr1	S21	>1	1.5754200	GHz	30.649	dB	
(Cg1	Tr1	S21	2	1.6054200	GHz	-6.7098	dB	
(Cg1	Tr1	S21	3	1.5454200	GHz	24.584	dB	
(Cg1	Tr1	S21	4	1.6254200	GHz	-5.6354	dB	
(Cg1	Tr1	S21	5	1.5254200	GHz	8.0734	dB	
(Cg1	Tr1	S21	6	1.6754200	GHz	-15.436	dB	
(Cg1	Tr1	S21	7	1.4754200	GHz	-1.5714	dB	






7.2 Noise Figure









8. Drawing (Unit: mm)







Side View




	Name	Material	Finish	QTY
1	Housing	PC	Black	1
2	Closed Cell Foam	CR 4305	Black	1
3	3M Double Adhesive	3M 9448 HK	White Liner	1
4	Metal Base	Zinc Alloy	Ni Plated	1
5	Rubber Stopper	Silicone Rubber	Black	1
6	Outer Nut Cover	ASA	Black	1
7	M18 Inner Nut	Steel Carbon	Zn Plated	1
8	Heat Shrink Tube (GPS)	PE	Blue Tube/White Text	1
9	Heat Shrink Tube (FirstNet)	PE	Red Tube/White Text	1
10	RG174 Coaxial Cable	PVC	Black	1
11	TGC200 Coaxial Cable	PE	Black	1
12	SMA(M)ST for RG174	Brass	Au Plated	1
13	SMA(M)ST for TGC200	Brass	Au Plated	1





9. Installation




Recommended torque for Mounting is 24.5N·m Maximum torque for mounting is 29.4N·m







10. Packaging







Taoglas makes no warranties based on the accuracy or completeness of the contents of this document and reserves the right to make changes to specifications and product descriptions at any time without notice. Taoglas reserves all rights to this document and the information contained herein.

Reproduction, use or disclosure to third parties without express permission is strictly prohibited.

Copyright © Taoglas Ltd.