Achieving the best system cost in Mid/High Power

Mid-Power LED - 3030 Series S1W0-3030XX9003-00000000-00001 (Cool, Neutral, Warm)


















Product Brief

Description

- This White Colored surface-mount LED comes in standard package dimension.
 Package Size: 3.3x3.0x0.75mm
- It has a substrate made up of a molded plastic reflector sitting on top of a lead frame
- The die is attached within the reflector cavity and the cavity is encapsulated by silicone.
- The package design coupled with careful selection of component materials allow these products to perform with high reliability.

Featu es and Benefits

- Thermally Enhanced Package Design
- Mid Power to High Power up to 0.6W
- Max. Driving Current 200mA
- Compact Package Size
- High Color Quality with CRI Min.90
- Pb-free Reflow Soldering Application

Key Applications

- Replacement lamps Bulb, Tube
- Commercial
- Industrial
- Residential

Table 1. Product Selection Table

Reference	Calan	Nominal	Dord Noveleau	CRI
Code	Color	ССТ	Part Number	Min
		6500K	S1W0-3030659003-00000000-00001	
	Cool White	5700K	S1W0-3030579003-00000000-00001	
		5000K	S1W0-3030509003-00000000-00001	•
STW9C12C-E0	Neutral White	4000K	S1W0-3030409003-00000000-00001	90
		3500K	S1W0-3030359003-00000000-00001	•
	Warm White	3000K	S1W0-3030309003-00000000-00001	•
			2700K	S1W0-3030279003-00000000-00001



Table of Contents

Ind	ex	
•	Product Brief	1
•	Table of Contents	2
•	Performance Characteristics	3
•	Characteristics Graph	5
•	Color Bin Structure	11
•	Mechanical Dimensions	15
•	Recommended Solder Pad	16
•	Reflow Soldering Characteristics	17
•	Emitter Tape & Reel Packaging	18
•	Product Nomenclature	20
•	Handling of Silicone Resin for LEDs	21
•	Precaution For Use	22
•	Company Information	25

Performance Characteristics

Table 2. Product Selection Guide, $I_F = 65 \text{mA}$, $T_j = 25^{\circ}\text{C}$, RH30%

Min. CRI, R _a	Nominal CCT [K] ^[1]	Min. Flux [lm]	Typ. Luminous Flux Φ _v ^[2] [lm] @65mA	Typ. Luminous Efficacy [lm/W] @65mA	Part Number
	6500	27.0	28.8	164	S1W0-3030659003- 00000000-00001
	5700	28.5	29.4	168	S1W0-3030579003- 00000000-00001
	5000	28.5	30.2	172	\$1W0-3030509003- 00000000-00001
90	4000	28.5	29.8	170	S1W0-3030409003- 00000000-00001
	3500	28.5	29.2	166	S1W0-3030359003- 00000000-00001
	3000	27.0	28.6	163	S1W0-3030309003- 00000000-00001
	2700	27.0	28.2	161	S1W0-3030279003- 00000000-00001

Notes:

Rev 0.6, Aug, 2020 www.seoulsemicon.com

⁽¹⁾ Correlated Color Temperature is derived from the CIE 1931 Chromaticity diagram.

⁽²⁾ Seoul Semiconductor maintains a tolerance of $\pm 7\%$ on flux and power measurements.



Performance Characteristics

Table 3. Characteristics, I_F=65mA, T_i= 25°C, RH30%

Parramatan.	Symbol	Value			11-24
Parameter		Min.	Тур.	Max ^[6] .	Unit
Forward Current	I _F	-	65	-	mA
Forward Voltage ^[1]	V _F	2.6	2.7	2.8	V
CRI ^[1]	R _a	90		100	
Viewing Angle [2]	2O _{1/2}	-	120	70	Deg.
Thermal resistance (J to S) [3]	Rθ _{J-S}	-	7.5	0	°C/W
ESD Sensitivity(HBM) [4]	-		Class 3A J	EDEC JS-001-2	2017

Table 4. Absolute Maximum Ratings^[6]

Parameter	Symbol	Value	Unit
Forward Current	l _F	200	mA
Power Dissipation	P_{D}	0.6	W
Junction Temperature ^[5]	T _j	125	°C
Operating Temperature	T _{opr}	-40 ~ + 85	°C
Storage Temperature	T _{stg}	-40 ~ + 100	°C

Notes:

- (1) Tolerance : VF : \pm 0.1V, Flux : \pm 7%, Ra : \pm 2, x,y : \pm 0.005, R9 : \pm 6
- (2) $2\Theta_{1/2}$ is the off-axis where the luminous intensity is 1/2 of the peak intensity.
- (3) Thermal resistance : Rth_{JS} (Junction / solder)
- (4) A zener diode is included for ESD Protection.
- (5) $T_J = T_S + R\theta_{J-S} * P$
 - T_J [°C] = LED Junction Temperature
 - $T_S[^{\circ}C] = LED Solder Temperature$
 - $P[W] = I_F *V_F$
- (6) It is recommended to use it in the condition that the reliability is secured within the Max value.
 - Calculated performance values are for reference only
 - All measurements were made under the standardized environment of seoul semiconductor
- LED's properties might be different from suggested values like above and below tables if operation
 condition will be exceeded our parameter range. Care is to be taken that power dissipation does not
 exceed the absolute maximum rating of the product.
- Thermal resistance can be increased substantially depending on the heat sink design/operating condition, and the maximum possible driving current will decrease accordingly.
- All measurements were made under the standardized environment of Seoul Semiconductor.

Fig 1. Color Spectrum, T_i = 25°C




Fig 2. Radiant Pattern, T_i = 25°C




Fig 3. Forward Voltage vs. Forward Current, $T_j = 25^{\circ}C$




Fig 4. Forward Current vs. Relative Luminous Flux, $T_j = 25^{\circ}C$





Fig 5. Forward Current vs. CIE x, y Shift, T_i = 25°C






Fig 6. Junction Temperature vs. Relative Luminous Flux, I_F=65mA




Fig 7. Junction Temperature vs. Relative Forward Voltage, I_F=65mA





Fig 8. Chromaticity Coordinate vs. Junction Temperature, I_F=65mA







Fig 9. Ambient Temperature vs. Maximum Forward Current, $T_{i_max} = 125$ °C





Color Bin Structure

Table 5. Bin Code description, T_i=25°C, I_E=65mA

Part Number	Luminous Flux (lm)			Color	Typical Forward Voltage (V)		
	Bin Code	Min.	Max.	Chromaticity Coordinate	Bin Code	Min.	Max.
S1W0-3030X X9003-00000 000-00001	S0	27.0	28.5	Refer to	Y0	2.6	2.7
	S 5	28.5	30.0		Y1	2.7	2.8
	Т0	30.0	31.5	page.12			
	T5	31.5	33	•		0	

Table 6. Flux rank distribution

Available ranks

сст	CIE	Flux Rank				
6000- 7000K	А	S0	S 5	T0	T5	
5300- 6000K	В	S0	S 5	T0	T5	
4700 ~ 5300K	С	S0	S 5	ТО	T5	
3700 ~ 4200K	Е	S0	S 5	ТО	T5	
3200 ~ 3700K	F	S0	S 5	T0	T5	
2900 ~ 3200K	G	S0	S 5	T0	T5	
2600 ~ 2900K	Н	S0	S 5	T0	T5	


*Notes:

All measurements were made under the standardized environment of Seoul Semiconductor. In order to ensure availability, single color rank will not be orderable.

Color Bin Structure


Kitting Solution of 8 sub bins

In multi-LED applications, creating a MacAdam 2-step/3-step from a variety of 4bins is a effective way to achieve good color quality while minimizing LED costs. In the below illustration, you will find how we can achieve the macadam 2-step/3-step using kitting 3-step/4-step ellipse bins.



Color Bin Structure

CIE Chromaticity Diagram (Cool white), T_i=25°C, I_F=65mA




5700K 3Step 5000K 3Step 6500K 3Step Center point 0.3123: 0.3282 Center point 0.3287: 0.3417 Center point 0.3447 : 0.3553 Major Axis a 0.0066 Major Axis a 0.0071 Major Axis a 0.0081 Minor Axis b 0.0027 Minor Axis b 0.0030 Minor Axis b 0.0035 Ellipse Ellipse Ellipse 58 59 60 **Rotation Angle** Rotation Angle Rotation Angle

6500K	4Step	5700	K 4Step	5000K 4Step		
4	A		4B	4C		
Center point	0.3123 : 0.3282	Center point	0.3287 : 0.3417	Center point	0.3447 : 0.3553	
Major Axis a	0.0088	Major Axis a	0.0095	Major Axis a	0.0108	
Minor Axis b	0.0036	Minor Axis b	0.0040	Minor Axis b	0.0047	
Ellipse Rotation Angle	58	Ellipse Rotation Angle	59	Ellipse Rotation Angle	60	

Α	A	А	В	Α	С	Α	D
CIE X	CIE Y						
0.3028	0.3304	0.3115	0.3393	0.3131	0.329	0.3048	0.3209
0.3048	0.3209	0.3131	0.329	0.3146	0.3187	0.3068	0.3113
0.3131	0.329	0.3213	0.3371	0.3221	0.3261	0.3146	0.3187
0.3115	0.3393	0.3205	0.3481	0.3213	0.3371	0.3131	0.329
В	A	В	В	В	C	В	D
CIE X	CIE Y						
0.3207	0.3462	0.3292	0.3539	0.3293	0.3423	0.3215	0.3353
0.3215	0.3353	0.3293	0.3423	0.3294	0.3306	0.3222	0.3243
0.3293	0.3423	0.3371	0.3493	0.3366	0.3369	0.3294	0.3306
0.3292	0.3539	0.3376	0.3616	0.3371	0.3493	0.3293	0.3423
С	A	c	В	c	C	С	D
CIE X	CIE Y						
0.3376	0.3616	0.3463	0.3687	0.3452	0.3558	0.3371	0.3493
0.3371	0.3493	0.3452	0.3558	0.344	0.3428	0.3366	0.3369
0.3452	0.3558	0.3533	0.3624	0.3514	0.3487	0.344	0.3428
0.3463	0.3687	0.3551	0.376	0.3533	0.3624	0.3452	0.3558

Color Bin Structure

CIE Chromaticity Diagram (Neutral white), T_i=25°C, I_F=65mA



4000K 3Step

	3E		
Center point	0.3818 : 0.3797		
Major Axis a	0.0094		
Minor Axis b	0.0040		
Ellipse	53		
Rotation Angle	55		


4000K 4Step

4E						
Center point	0.3818 : 0.3797					
Major Axis a	0.0125					
Minor Axis b	0.0053					
Ellipse	53					
Rotation Angle	55					

E	Α	E	В	E	c	E	D
CIE X	CIE Y						
0.3736	0.3874	0.3871	0.3959	0.3828	0.3803	0.3703	0.3726
0.3703	0.3726	0.3828	0.3803	0.3784	0.3647	0.367	0.3578
0.3828	0.3803	0.3952	0.388	0.3898	0.3716	0.3784	0.3647
0.3871	0.3959	0.4006	0.4044	0.3952	0.388	0.3828	0.3803

Color Bin Structure

CIE Chromaticity Diagram (Warm white), T_i=25°C, I_F=65mA




3500K 3Step 3000K 3Step 2700K 3Step 3H **3G** 0.4073: 0.3917 0.4338: 0.4030 0.4578: 0.4101 Center point Center point Center point Major Axis a 0.0093 Major Axis a Major Axis a 0.0079 0.0085 Minor Axis b 0.0041 Minor Axis b 0.0041 Minor Axis b 0.0041 Ellipse Ellipse Ellipse 53 53 54 **Rotation Angle** Rotation Angle **Rotation Angle**

CIE x

3500K 4Step 4F		3000	K 4Step	2700K 4Step		
		4G			4H	
	Center point	0.4073 : 0.3917	Center point	0.4338 : 0.4030	Center point	0.4578 : 0.4101
	Major Axis a	0.0124	Major Axis a	0.0113	Major Axis a	0.0105
	Minor Axis b	0.0055	Minor Axis b	0.0055	Minor Axis b	0.0055
	Ellipse Rotation Angle	53	Ellipse Rotation Angle	53	Ellipse Rotation Angle	54

	FA	F	В	F	С	F	D
CIE X	CIE Y						
0.3996	0.4015	0.4146	0.4089	0.4082	0.392	0.3943	0.3853
0.3943	0.3853	0.4082	0.392	0.4017	0.3751	0.3889	0.369
0.4082	0.392	0.4223	0.399	0.4147	0.3814	0.4017	0.3751
0.4146	0.4089	0.4299	0.4165	0.4223	0.399	0.4082	0.392
	GA	G	В	G	C	G	D
CIE X	CIE Y						
0.4299	0.4165	0.443	0.4212	0.4345	0.4033	0.4223	0.399
0.4223	0.399	0.4345	0.4033	0.4259	0.3853	0.4147	0.3814
0.4345	0.4033	0.4468	0.4077	0.4373	0.3893	0.4259	0.3853
0.443	0.4212	0.4562	0.426	0.4468	0.4077	0.4345	0.4033
	HA	н	В	н	C	H	D
CIE X	CIE Y						
0.4562	0.426	0.4687	0.4289	0.4585	0.4104	0.4468	0.4077
0.4468	0.4077	0.4585	0.4104	0.4483	0.3919	0.4373	0.3893
0.4585	0.4104	0.4703	0.4132	0.4593	0.3944	0.4483	0.3919
0.4687	0.4289	0.481	0.4319	0.4703	0.4132	0.4585	0.4104

Mechanical Dimensions




(1) All dimensions are in millimeters.

(2) Scale: none

(3) Undefined tolerance is $\pm 0.07 \text{mm}$

Recommended Solder Pad



Notes:

- (1) All dimensions are in millimeters.
- (2) Scale: none
- (3) This drawing without tolerances are for reference only
- (4) Undefined tolerance is $\pm 0.1 \text{mm}$

Reflow Soldering Characteristics





Table 7.


Profile Feature	Sn-Pb Eutectic Assembly	Pb-Free Assembly
Average ramp-up rate (Tsmax to Tp)	3° C/second max.	3° C/second max.
Preheat - Temperature Min (Tsmin) - Temperature Max (Tsmax) - Time (Tsmin to Tsmax) (ts)	100 °C 150 °C 60-120 seconds	150 °C 200 °C 60-180 seconds
Time maintained above: - Temperature (TL) - Time (tL)	183 °C 60-150 seconds	217 °C 60-150 seconds
Peak Temperature (Tp)	215℃	260℃
Time within 5°C of actual Peak Temperature (tp)2	10-30 seconds	20-40 seconds
Ramp-down Rate	6 °C/second max.	6 °C/second max.
Time 25°C to Peak Temperature	6 minutes max.	8 minutes max.

Caution

- (1) Reflow soldering is recommended not to be done more than two times. In the case of more than 24 hours passed soldering after first, LEDs will be damaged.
- (2) Repairs should not be done after the LEDs have been soldered. When repair is unavoidable, suitable tools must be used.
- (3) Die slug is to be soldered.
- (4) When soldering, do not put stress on the LEDs during heating.
- (5) After soldering, do not warp the circuit board.

Emitter Tape & Reel Packing






- (1) Quantity: 4,000pcs/Reel
- (2) Cumulative Tolerance : Cumulative Tolerance/10 pitches to be ± 0.2 mm
- (3) Adhesion Strength of Cover Tape
 Adhesion strength to be 0.1-0.7N when the cover tape is turned off from the carrier tape at the angle of 10° to the carrier tape.
- (4) Package: P/N, Manufacturing data Code No. and Quantity to be indicated on a damp proof Package.



Emitter Tape & Reel Packing



Product Nomenclature

Table 8. Part Numbering System : $X_1X_2X_3X_4X_5X_6X_7X_8-X_9X_{10}$

Part Number Code	Description	Part Number	Value
X ₁	Company	S	
X ₂	Top View LED series	Т	
X_3X_4	Color Specification	W9	CRI 90
X ₅	Package series	С	C series
X ₆ X ₇	Characteristic code	12	70
X ₈	Revision	С	0
X ₉ X ₁₀	X ₉ X ₁₀ Characteristic		

Part Number Code	Description	Part Number	Value
X ₁	Company	S	Seoul Semiconductor
X ₂	Level of Integration	1	Discrete LED
X ₃ X ₄	Technology	WO	General White
X ₅ X ₆ X ₇ X ₈	Dimension	3030	
X ₉ X ₁₀	CCT	xx	
X ₁₁ X ₁₂	CRI	90	
X ₁₃ X ₁₄	Vf	03	
X ₁₅ X ₁₆ X ₁₇	Characteristic code Flux Rank	000	
X ₁₈ X ₁₉ X ₂₀	Characteristic code Vf Rank	000	
X ₂₁ X ₂₂	Characteristic code Color Step	00	
X ₂₃ X ₂₄	Туре	00	
X ₂₅ X ₂₆ X ₂₇	Internal code	001	

Table 9. Lot Numbering System :Y₁Y₂Y₃Y₄Y₅Y₆Y₇Y₈Y₉Y₁₀-Y₁₁Y₁₂Y₁₃Y₁₄Y₁₅Y₁₆Y₁₇

Lot Number Code	Description	Lot Number	Value
Y ₁ Y ₂	Year		
Y ₃	Month		
Y ₄ Y ₅	Day		
Y ₆	Top View LED series		
Y ₇ Y ₈ Y ₉ Y ₁₀ Mass order			
Y ₁₁ Y ₁₂ Y ₁₃ Y ₁₄ Y ₁₅ Y ₁₆ Y ₁₇	Internal Number		




Handling of Silicone Resin for LEDs

(1) During processing, mechanical stress on the surface should be minimized as much as possible. Sharp objects of all types should not be used to pierce the sealing compound.



(2) In general, LEDs should only be handled from the side. By the way, this also applies to LEDs without a silicone sealant, since the surface can also become scratched.



- (3) When populating boards in SMT production, there are basically no restrictions regarding the form of the pick and place nozzle, except that mechanical pressure on the surface of the resin must be prevented. This is assured by choosing a pick and place nozzle which is larger than the LED's reflector area.
- (4) Silicone differs from materials conventionally used for the manufacturing of LEDs. These conditions must be considered during the handling of such devices. Compared to standard encapsulants, silicone is generally softer, and the surface is more likely to attract dust.

As mentioned previously, the increased sensitivity to dust requires special care during processing. In cases where a minimal level of dirt and dust particles cannot be guaranteed, a suitable cleaning solution must be applied to the surface after the soldering of components.

- (5) SSC suggests using isopropyl alcohol for cleaning. In case other solvents are used, it must be assured that these solvents do not dissolve the package or resin.

 Ultrasonic cleaning is not recommended. Ultrasonic cleaning may cause damage to the LED.
- (6) Please do not mold this product into another resin (epoxy, urethane, etc) and do not handle this. product with acid or sulfur material in sealed space.



Precaution for Use

(1) Storage

To avoid the moisture penetration, we recommend store in a dry box with a desiccant.

The recommended storage temperature range is 5°C to 30°C and a maximum humidity of RH50%.

(2) Use Precaution after Opening the Packaging

Use SMT techniques properly when you solder the LED as separation of the lens may affect the light output efficiency.

Pay attention to the following:

- a. Recommend conditions after opening the package
 - Sealing
 - Temperature : 5 ~ 40°C Humidity : less than RH30%
- b. If the package has been opened more than 4 week(MSL_2a) or the color of the desiccant changes, components should be dried for 10-12hr at 60±5°C
- (3) Do not apply mechanical force or excess vibration during the cooling process to normal temperature after soldering.
- (4) Do not rapidly cool device after soldering.
- (5) Components should not be mounted on warped (non coplanar) portion of PCB.
- (6) Radioactive exposure is not considered for the products listed here in.
- (7) Gallium arsenide is used in some of the products listed in this publication.
 These products are dangerous if they are burned or shredded in the process of disposal.
 It is also dangerous to drink the liquid or inhale the gas generated by such products when chemically disposed of.
- (8) This device should not be used in any type of fluid such as water, oil, organic solvent and etc. When washing is required, IPA (Isopropyl Alcohol) should be used.
- (9) When the LEDs are in operation the maximum current should be decided after measuring the package temperature.

Precaution for Use

- (10) The appearance and specifications of the product may be modified for improvement without notice.
- (11) Long time exposure of sunlight or occasional UV exposure will cause lens discoloration.
- (12) VOCs (Volatile organic compounds) emitted from materials used in the construction of fixtures can penetrate silicone encapsulants of LEDs and discolor when exposed to heat and photonic energy. The result can be a significant loss of light output from the fixture. Knowledge of the properties of the materials selected to be used in the construction of fixtures can help prevent these issues.
- (13) Attaching LEDs, do not use adhesives that outgas organic vapor.
- (14) The driving circuit must be designed to allow forward voltage only when it is ON or OFF.
 If the reverse voltage is applied to LED, migration can be generated resulting in LED damage.
- (15) Similar to most Solid state devices; LEDs are sensitive to Electro-Static Discharge (ESD) and Electrical Over Stress (EOS). Below is a list of suggestions that Seoul Semiconductor purposes to minimize these effects.
- a. ESD (Electro Static Discharge)

Electrostatic discharge (ESD) is the defined as the release of static electricity when two objects come into contact. While most ESD events are considered harmless, it can be an expensive problem in many industrial environments during production and storage. The damage from ESD to an LEDs may cause the product to demonstrate unusual characteristics such as:

- Increase in reverse leakage current lowered turn-on voltage
- Abnormal emissions from the LED at low current

The following recommendations are suggested to help minimize the potential for an ESD event. One or more recommended work area suggestions:

- Ionizing fan setup
- ESD table/shelf mat made of conductive materials
- ESD safe storage containers

One or more personnel suggestion options:

- Antistatic wrist-strap
- Antistatic material shoes
- Antistatic clothes

Environmental controls:

- Humidity control (ESD gets worse in a dry environment)



Precaution for Use

b. EOS (Electrical Over Stress)

Electrical Over-Stress (EOS) is defined as damage that may occur when an electronic device is subjected to a current or voltage that is beyond the maximum specification limits of the device. The effects from an EOS event can be noticed through product performance like:

- Changes to the performance of the LED package
 (If the damage is around the bond pad area and since the package is completely encapsulated the package may turn on but flicker show severe performance degradation.)
- Changes to the light output of the luminaire from component failure
- Components on the board not operating at determined drive power

Failure of performance from entire fixture due to changes in circuit voltage and current across total circuit causing trickle down failures. It is impossible to predict the failure mode of every LED exposed to electrical overstress as the failure modes have been investigated to vary, but there are some common signs that will indicate an EOS event has occurred:

- Damaged may be noticed to the bond wires (appearing similar to a blown fuse)
- Damage to the bond pads located on the emission surface of the LED package (shadowing can be noticed around the bond pads while viewing through a microscope)
- Anomalies noticed in the encapsulation and phosphor around the bond wires.
- This damage usually appears due to the thermal stress produced during the EOS event.
- c. To help minimize the damage from an EOS event Seoul Semiconductor recommends utilizing:
 - A surge protection circuit
 - An appropriately rated over voltage protection device
 - A current limiting device



Company Information

Published by

Seoul Semiconductor © 2013 All Rights Reserved.

Company Information

Seoul Semiconductor (www.SeoulSemicon.com) manufacturers and packages a wide selection of light emitting diodes (LEDs) for the automotive, general illumination/lighting, Home appliance, signage and back lighting markets. The company is the world's fifth largest LED supplier, holding more than 10,000 patents globally, while offering a wide range of LED technology and production capacity in areas such as "nPola", "Acrich", the world's first commercially produced AC LED, and "Acrich MJT - Multi-Junction Technology" a proprietary family of high-voltage LEDs.

The company's broad product portfolio includes a wide array of package and device choices such as Acrich and Acirch2, high-brightness LEDs, mid-power LEDs, side-view LEDs, and through-hole type LEDs as well as custom modules, displays, and sensors.

Legal Disclaimer

Information in this document is provided in connection with Seoul Semiconductor products. With respect to any examples or hints given herein, any typical values stated herein and/or any information regarding the application of the device, Seoul Semiconductor hereby disclaims any and all warranties and liabilities of any kind, including without limitation, warranties of non-infringement of intellectual property rights of any third party. The appearance and specifications of the product can be changed to improve the quality and/or performance without notice.