

FEATURES

SCBS718D-JUNE 2000-REVISED DECEMBER 2006

F	EATURES	SN54LVT162244A WD PACKAGE
•	Members of the Texas Instruments Widebus™ Family	SN74LVT162244ADGG, DGV, OR DL PACKAGE (TOP VIEW)
•	Output Ports Have Equivalent 22-Ω Series Resistors, So No External Resistors Are Required	10E 1 48] 20E 1Y1 2 47] 1A1
•	Support Mixed-Mode Signal Operation (5-V Input and Output Voltages With 3.3-V V <sub>CC</sub> )	1Y2 0 3 46 0 1A2 GND 0 4 45 0 GND 1Y3 0 5 44 0 1A3
•	Support Unregulated Battery Operation Down to 2.7 V	$\begin{array}{cccccccccccccccccccccccccccccccccccc$
•	Typical V <sub>OLP</sub> (Output Ground Bounce) <0.8 V at V <sub>CC</sub> = 3.3 V, T <sub>A</sub> = 25°C	2Y1 [ 8 41 ] 2A1 2Y2 [ 9 40 ] 2A2
•	I <sub>off</sub> and Power-Up 3-State Support Hot Insertion	GND [] 10 39 ]] GND 2Y3 [] 11 38 [] 2A3
•	Distributed V <sub>CC</sub> and GND Pins Minimize High-Speed Switching Noise	2Y4 0 12 37 0 2A4 3Y1 0 13 36 0 3A1
•	Flow-Through Architecture Optimizes PCB Layout	3Y2   14 35   3A2 GND   15 34   GND
•	Latch-Up Performance Exceeds 100 mA Per JESD 78, Class II	3Y3 [] 16 33 [] 3A3 3Y4 [] 17 32 [] 3A4 V <sub>CC</sub> [] 18 31 [] V <sub>CC</sub>
٠	ESD Protection Exceeds JESD 22	4Y1 [] 19 30 ]] 4A1
	<ul> <li>2000-V Human-Body Model (A114-A)</li> </ul>	4Y2 🛛 20 29 🛛 4A2
	<ul> <li>200-V Machine Model (A115-A)</li> </ul>	GND 21 28 GND
	<ul> <li>1000-V Charged-Device Model (C101)</li> </ul>	4Y3 22 27 4A3
		4Y4 23 26 4A4
		40E 24 25 30E

### **DESCRIPTION/ORDERING INFORMATION**

The 'LVT162244A devices are 16-bit buffers and line drivers designed for low-voltage (3.3-V) V<sub>CC</sub> operation, but with the capability to provide a TTL interface to a 5-V system environment. These devices can be used as four 4-bit buffers, two 8-bit buffers, or one 16-bit buffer. These devices provide true outputs and symmetrical active-low output-enable  $(\overline{OE})$  inputs.

The outputs, which are designed to source or sink up to 12 mA, include equivalent 22- $\Omega$  series resistors to reduce overshoot and undershoot.

When  $V_{CC}$  is between 0 and 1.5 V, the devices are in the high-impedance state during power up or power down. However, to ensure the high-impedance state above 1.5 V,  $\overline{OE}$  should be tied to V<sub>CC</sub> through a pullup resistor; the minimum value of the resistor is determined by the current-sinking capability of the driver.

These devices are fully specified for hot-insertion applications using loff and power-up 3-state. The loff circuitry disables the outputs, preventing damaging current backflow through the devices when they are powered down. The power-up 3-state circuitry places the outputs in the high-impedance state during power up and power down, which prevents driver conflict.



Please be aware that an important notice concerning availability, standard warranty, and use in critical applications of Texas Instruments semiconductor products and disclaimers thereto appears at the end of this data sheet. Widebus is a trademark of Texas Instruments.

SCBS718D-JUNE 2000-REVISED DECEMBER 2006

### TEXAS INSTRUMENTS www.ti.com

### **DESCRIPTION/ORDERING INFORMATION (CONTINUED)**

<b>T</b> <sub>A</sub> −40°C to 85°C	PACKA	GE <sup>(1)</sup>	ORDERABLE PART NUMBER	TOP-SIDE MARKING		
	FBGA – GRD	Reel of 1000	SN74LVT162244AGRDR	LZ244A		
	FBGA – ZRD (Pb-free)	Reel 01 1000	SN74LVT162244AZRDR	- LZ244A		
		Tube of 25	SN74LVT162244ADL			
	SSOP – DL	TUDE OF 25	SN74LVT162244ADLG4	LVT162244A		
	330P - DL	Reel of 1000	SN74LVT162244ADLR	LV1102244A		
40°C to 95°C		Reel 01 1000	74LVT162244ADLRG4			
-40°C 10 85°C	TSSOP – DGG	Reel of 2000	SN74LVT162244ADGGR	LVT162244A		
	1330F - DGG	Reel 01 2000	74LVT162244ADGGRE4	LV1102244A		
	TVSOP – DGV	Reel of 2000	SN74LVT162244ADGVR	LZ244A		
	TVSOP – DGV	Reel 01 2000	74LVT162244ADGVRE4	- LZ244A		
	VFBGA – GQL	Reel of 1000	SN74LVT162244AGQLR	LZ244A		
	VFBGA – ZQL	Reel OF 1000	SN74LVT162244AZQLR			
–55°C to 125°C	CFP – WD	Tube	SNJ544LVT162244AWD <sup>(2)</sup>	SNJ54LVT162244AWD		

#### **ORDERING INFORMATION**

(1) Package drawings, standard packing quantities, thermal data, symbolization, and PCB design guidelines are available at www.ti.com/sc/package.

(2) Product preview

G	QL	OR (T(	ZQ OP				GE
	_	12	3	4	5	6	_
A B C D E F G							
H J K	Ċ		Ö	Ö	0	Ö	J

#### TERMINAL ASSIGNMENTS<sup>(1)</sup> (56-Ball GQL/ZQL Package)

	1	2	3	4	5	6
Α	1 <del>0E</del>	NC	NC	NC	NC	2 <mark>0E</mark>
В	1Y2	1Y1	GND	GND	1A1	1A2
С	1Y4	1Y3	V <sub>CC</sub>	V <sub>CC</sub>	1A3	1A4
D	2Y2	2Y1	GND GND		2A1	2A2
Е	2Y4	2Y3			2A3	2A4
F	3Y1	3Y2			3A2	3A1
G	3Y3	3Y4	GND	GND	3A4	3A3
Н	4Y1	4Y2	V <sub>CC</sub>	V <sub>CC</sub>	4A2	4A1
J	4Y3	4Y4	GND	GND	4A4	4A3
к	4 <del>0E</del>	NC	NC	NC	NC	3 <mark>0E</mark>

(1) NC – No internal connection



SCBS718D-JUNE 2000-REVISED DECEMBER 2006

#### GRD OR ZRD PACKAGE (TOP VIEW)

		1	2	3	4	5	6	
Α	$\langle$	$\bigcirc$	$\bigcirc$	$\bigcirc$	$\bigcirc$	$\bigcirc$	$\bigcirc$	
в				$\bigcirc$				
С		$\bigcirc$	$\bigcirc$	$\bigcirc$	$\bigcirc$	$\bigcirc$	$\bigcirc$	
D		$\bigcirc$	$\bigcirc$	$\bigcirc$	$\bigcirc$	$\bigcirc$	$\bigcirc$	
Е		$\bigcirc$	$\bigcirc$	$\bigcirc$	$\bigcirc$	$\bigcirc$	$\bigcirc$	
F		$\bigcirc$	$\bigcirc$	$\bigcirc$	$\bigcirc$	$\bigcirc$	$\bigcirc$	
G		$\bigcirc$	$\bigcirc$	$\bigcirc$	$\bigcirc$	$\bigcirc$	$\bigcirc$	
н		$\bigcirc$	$\bigcirc$	$\bigcirc$	$\bigcirc$	$\bigcirc$	$\bigcirc$	
J		$\bigcirc$	$\bigcirc$	$\bigcirc$	$\bigcirc$	$\bigcirc$	$\bigcirc$	

(54	-Ball G	1Y2         NC         NC         1A2         1A3			
1	2	3	4	5	6
1Y1	NC	1 <del>0E</del>	2 <mark>0E</mark>	NC	1A1
1Y3	1Y2	NC	NC	1A2	1A3
2Y1	1Y4	Voo	Vaa	1A4	2A1

TERMINAL ASSIGNMENTS<sup>(1)</sup>

С	2Y1	1Y4	V <sub>CC</sub>	V <sub>CC</sub>	1A4	2A1
D	2Y3	2Y2	GND	GND	2A2	2A3
E	3Y1	2Y4	GND	GND	2A4	3A1
F	3Y3	3Y2	GND	GND	3A2	3A3
G	4Y1	3Y4	V <sub>CC</sub>	V <sub>CC</sub>	3A4	4A1
н	4Y3	4Y2	NC	NC	4A2	4A3
J	4Y4	NC	4 <del>0E</del>	3 <del>0E</del>	NC	4A4

(1) NC – No internal connection


# FUNCTION TABLE (each 4-bit buffer/driver)

A B

INPL	JTS	OUTPUT
ŌĒ	Α	Y
L	Н	Н
L	L	L
н	Х	Z

SCBS718D-JUNE 2000-REVISED DECEMBER 2006





Pin numbers shown are for the DGG, DGV, DL, and WD packages.

### Absolute Maximum Ratings<sup>(1)</sup>

over operating free-air temperature range (unless otherwise noted)

			MIN	MAX	UNIT
V <sub>CC</sub>	Supply voltage range		-0.5	4.6	V
VI	Input voltage range <sup>(2)</sup>		-0.5	7	V
Vo	Voltage range applied to any output in the high-	impedance or power-off state <sup>(2)</sup>	-0.5	7	V
Vo	Voltage range applied to any output in the high	state <sup>(2)</sup>	-0.5	V <sub>CC</sub> + 0.5	V
I <sub>O</sub>	Current into any output in the low state			30	mA
I <sub>O</sub>	Current into any output in the high state <sup>(3)</sup>	rent into any output in the high state <sup>(3)</sup>		30	mA
I <sub>IK</sub>	Input clamp current	V <sub>I</sub> < 0		-50	mA
I <sub>OK</sub>	Output clamp current	V <sub>O</sub> < 0		-50	mA
		DGG package		70	
		DGV package		58	
$\theta_{JA}$	Package thermal impedance <sup>(4)</sup>	DL package		63	°C/W
		GQL/ZQL package		42	
		GRD/ZRD package		-0.5 7 -0.5 7 -0.5 V <sub>CC</sub> + 0.5 30 30 -50 -50 70 58 63	
T <sub>stg</sub>	Storage temperature range		-65	150	°C

(1) Stresses beyond those listed under "absolute maximum ratings" may cause permanent damage to the device. These are stress ratings only, and functional operation of the device at these or any other conditions beyond those indicated under "recommended operating conditions" is not implied. Exposure to absolute-maximum-rated conditions for extended periods may affect device reliability.

The input and output negative-voltage ratings may be exceeded if the input and output clamp-current ratings are observed. (2)

(3) This current flows only when the output is in the high state and  $V_0 > V_{CC}$ . (4) The package thermal impedance is calculated in accordance with JESD 51-7.

**Recommended Operating Conditions**<sup>(1)</sup>

			SN54LVT162	244A <sup>(2)</sup>	SN74LVT1	62244A	UNIT	
			MIN	MAX	MIN	MAX		
V <sub>CC</sub>	Supply voltage		2.7	3.6	2.7	3.6	V	
V <sub>IH</sub>	High-level input voltage		2		2		V	
V <sub>IL</sub>	Low-level input voltage			0.8		0.8	V	
VI	Input voltage			5.5		5.5	V	
I <sub>OH</sub>	High-level output current			-12		-12	mA	
I <sub>OL</sub>	Low-level output current			12		12	mA	
$\Delta t / \Delta v$	Input transition rise or fall rate	Outputs enabled		10		10	ns/V	
$\Delta t\!/\!\Delta V_{CC}$	Power-up ramp rate	· ·	200		200		μs/V	
T <sub>A</sub>	Operating free-air temperature		-55	125	-40	85	°C	

All unused inputs of the device must be held at V<sub>CC</sub> or GND to ensure proper device operation. Refer to the TI application report, Implications of Slow or Floating CMOS Inputs, literature number SCBA004.

(2) Product preview

SCBS718D-JUNE 2000-REVISED DECEMBER 2006

#### **Electrical Characteristics**

V<sub>IK</sub>

V<sub>OH</sub>

VOL

I<sub>L</sub>

 $I_{off}$ 

I<sub>OZH</sub>

I<sub>OZL</sub>

**I**OZPU

**I**OZPD

I<sub>CC</sub>

Ci

 $C_{o}$ 

 $\Delta I_{CC}{}^{(4)}$ 

over recommended operating free-air temperature range (unless otherwise noted)

		TEST	ONDITIONS	SN54I	LVT162244		SN74	LVT16224	4A	LINUT
	PARAMETER	TESTC	ONDITIONS	MIN	TYP <sup>(2)</sup>	MAX	MIN	TYP <sup>(2)</sup>	MAX	UNIT
		V <sub>CC</sub> = 2.7 V,	I <sub>I</sub> = -18 mA			-1.2			-1.2	V
		V <sub>CC</sub> = 3 V,	I <sub>OH</sub> = -12 mA	2						V
		$V_{CC} = 3 V,$	I <sub>OL</sub> = 12 mA			0.8			0.8	V
		V <sub>CC</sub> = 0 or 3.6 V,	V <sub>I</sub> = 5.5 V			10			10	
	Control inputs	V <sub>CC</sub> = 3.6 V,	$V_{I} = V_{CC} \text{ or } GND$			±1			±1	۵
	Data innuta	<u> </u>	$V_{I} = V_{CC}$			1			1	μA
	Data inputs	$V_{CC} = 3.6 V$	V <sub>1</sub> = 0			-5			-5	
		$V_{CC} = 0,$	$V_{I}$ or $V_{O} = 0$ to 4.5 V						±100	μA
+	I	V <sub>CC</sub> = 3.6 V,	$V_0 = 3 V$			5			5	μA
		V <sub>CC</sub> = 3.6 V,	$V_{0} = 0.5 V$			-5			-5	μA
F	บ	$\frac{V_{CC}}{OE}$ = 0 to 1.5 V, V <sub>O</sub> OE = don't care	= 0.5 V to 3 V,			±100 <sup>(3)</sup>			±100	μΑ
F	D	$\frac{V_{CC}}{OE}$ = 1.5 V to 0, V <sub>C</sub> $\overline{OE}$ = don't care	= 0.5 V to 3 V,			±100 <sup>(3)</sup>			±100	μΑ
		V <sub>CC</sub> = 3.6 V,	Outputs high			0.19			0.19	
		$I_{O} = 0,$	Outputs low			5			5	mA
		$V_{I} = V_{CC}$ or GND	Outputs disabled			0.19			0.19	
(	(4)	$V_{CC} = 3 V \text{ to } 3.6 V, 0$ V, Other inputs at V <sub>0</sub>	Dne input at V <sub>CC</sub> – 0.6 <sub>CC</sub> or GND			0.2			0.2	mA
		1								

SN54LVT162244A<sup>(1)</sup>

4

9

Texas

4

9

pF

pF

SN74LVT162244A

STRUMENTS www.ti.com

(1) Product preview

(2)

 $V_{I} = 3 V \text{ or } 0$ 

 $V_0 = 3 V \text{ or } 0$ 

All typical values are at  $V_{CC}$  = 3.3 V,  $T_A$  = 25°C. On products compliant to MIL-PRF-38535, this parameter is not production tested. (3)

(4) This is the increase in supply current for each input that is at the specified TTL voltage level, rather than  $V_{CC}$  or GND.

### **Switching Characteristics**

over recommended operating free-air temperature range,  $C_L = 50 \text{ pF}$  (unless otherwise noted) (see Figure 1)

			SN	SN54LVT162244A <sup>(1)</sup>				SN74LVT162244A				
PARAMETER	FROM (INPUT)	TO (OUTPUT)	V <sub>CC</sub> = 3.3 V ± 0.3 V		V <sub>CC</sub> = 2.7 V		V <sub>CC</sub> = 3.3 V ± 0.3 V			V <sub>CC</sub> = 2.7 V		UNIT
		(001101)	MIN	МАХ	MIN	МАХ	MIN	TYP <sup>(2</sup> )	МАХ	MIN	МАХ	
t <sub>PLH</sub>	•	Y	1.1	4.6		5.1	1.4	3.4	4		4.8	
t <sub>PHL</sub>	A	ř	1.1	3.9		4.5	1.2	2.9	3.6		4.1	ns
t <sub>PZH</sub>	OE	Y	1.1	5.4		6.7	1.2	3.9	5.1		6.5	ns
t <sub>PZL</sub>	OL	Ť	1.3	4.9		6.1	1.4	3.8	4.5		5.8	115
t <sub>PHZ</sub>	OE	Y	1.6	5.9		6.5	2.2	4.4	5		5.4	
t <sub>PLZ</sub>		ř	1	5.9		5.8	2	4.2	5		5.4	ns
t <sub>sk(LH)</sub>									0.5			20
t <sub>sk(HL)</sub>									0.5			ns

(1) Product preview

(2) All typical values are at  $V_{CC} = 3.3 \text{ V}$ ,  $T_A = 25^{\circ}\text{C}$ .

0 6 V **S1** O Open **500** Ω TEST **S**1 From Output Under Test O GND t<sub>PLH</sub>/t<sub>PHL</sub> Open t<sub>PLZ</sub>/t<sub>PZL</sub> 6 V  $C_{L} = 50 \text{ pF}$ **500** Ω t<sub>PHZ</sub>/t<sub>PZH</sub> GND (see Note A) 2.7 V LOAD CIRCUIT **Timing Input** 1.5 V 0 V tw t<sub>su</sub> t<sub>h</sub> 2.7 V 2.7 V 1.5 V 1.5 V Input 1.5 V 1.5 V **Data Input** • 0 V 0 V **VOLTAGE WAVEFORMS VOLTAGE WAVEFORMS** PULSE DURATION SETUP AND HOLD TIMES 2.7 V 2.7 V Output Input 1.5 V 1.5 V 1.5 V 1.5 V Control 0 V 0 V - t<sub>PLZ</sub> t<sub>PZL</sub>-t<sub>PHL</sub> t<sub>PLH</sub> Output VOH 3 V Waveform 1 Output 1.5 V 1.5 V 1.5 V S1 at 6 V V<sub>OL</sub> + 0.3 V (see Note B) VoL VoL t<sub>PHL</sub> t<sub>PLH</sub> t<sub>PZH</sub> t<sub>PHZ</sub> Output VOH V<sub>OH</sub> Waveform 2 V<sub>OH</sub> – 0.3 V Output 1.5 V 1.5 V 1.5 V S1 at GND ε0 V VoL (see Note B) **VOLTAGE WAVEFORMS VOLTAGE WAVEFORMS PROPAGATION DELAY TIMES** ENABLE AND DISABLE TIMES INVERTING AND NONINVERTING OUTPUTS LOW- AND HIGH-LEVEL ENABLING

#### PARAMETER MEASUREMENT INFORMATION

NOTES: A. C<sub>L</sub> includes probe and jig capacitance.

- B. Waveform 1 is for an output with internal conditions such that the output is low, except when disabled by the output control. Waveform 2 is for an output with internal conditions such that the output is high, except when disabled by the output control.
- C. All input pulses are supplied by generators having the following characteristics: PRR  $\leq$  10 MHz, Z<sub>O</sub> = 50  $\Omega$ , t<sub>f</sub>  $\leq$  2.5 ns, t<sub>f</sub>  $\leq$  2.5 ns.

D. The outputs are measured one at a time, with one transition per measurement.

#### Figure 1. Load Circuit and Voltage Waveforms



www.ti.com

4-May-2012

#### **PACKAGING INFORMATION**

Orderable Device	Status (1)	Package Type	Package Drawing	Pins	Package Qty	Eco Plan <sup>(2)</sup>	Lead/ Ball Finish	MSL Peak Temp <sup>(3)</sup>	Samples (Requires Login)
74LVT162244ADGGRE4	ACTIVE	TSSOP	DGG	48	2000	Green (RoHS & no Sb/Br)	CU NIPDAU	Level-1-260C-UNLIM	
74LVT162244ADGGRG4	ACTIVE	TSSOP	DGG	48	2000	Green (RoHS & no Sb/Br)	CU NIPDAU	Level-1-260C-UNLIM	
74LVT162244ADGVRE4	ACTIVE	TVSOP	DGV	48	2000	Green (RoHS & no Sb/Br)	CU NIPDAU	Level-1-260C-UNLIM	
74LVT162244ADGVRG4	ACTIVE	TVSOP	DGV	48	2000	Green (RoHS & no Sb/Br)	CU NIPDAU	Level-1-260C-UNLIM	
74LVT162244ADLRG4	ACTIVE	SSOP	DL	48	1000	Green (RoHS & no Sb/Br)	CU NIPDAU	Level-1-260C-UNLIM	
SN74LVT162244ADGGR	ACTIVE	TSSOP	DGG	48	2000	Green (RoHS & no Sb/Br)	CU NIPDAU	Level-1-260C-UNLIM	
SN74LVT162244ADGVR	ACTIVE	TVSOP	DGV	48	2000	Green (RoHS & no Sb/Br)	CU NIPDAU	Level-1-260C-UNLIM	
SN74LVT162244ADL	ACTIVE	SSOP	DL	48	25	Green (RoHS & no Sb/Br)	CU NIPDAU	Level-1-260C-UNLIM	
SN74LVT162244ADLG4	ACTIVE	SSOP	DL	48	25	Green (RoHS & no Sb/Br)	CU NIPDAU	Level-1-260C-UNLIM	
SN74LVT162244ADLR	ACTIVE	SSOP	DL	48	1000	Green (RoHS & no Sb/Br)	CU NIPDAU	Level-1-260C-UNLIM	
SN74LVT162244AGQLR	LIFEBUY	BGA MICROSTAR JUNIOR	GQL	56	1000	TBD	SNPB	Level-1-240C-UNLIM	
SN74LVT162244AGRDR	LIFEBUY	BGA MICROSTAR JUNIOR	GRD	54	1000	TBD	SNPB	Level-1-240C-UNLIM	
SN74LVT162244AZQLR	ACTIVE	BGA MICROSTAR JUNIOR	ZQL	56	1000	Green (RoHS & no Sb/Br)	SNAGCU	Level-1-260C-UNLIM	
SN74LVT162244AZRDR	ACTIVE	BGA MICROSTAR JUNIOR	ZRD	54	1000	Green (RoHS & no Sb/Br)	SNAGCU	Level-1-260C-UNLIM	

<sup>(1)</sup> The marketing status values are defined as follows: **ACTIVE:** Product device recommended for new designs.

### PACKAGE OPTION ADDENDUM



4-May-2012

LIFEBUY: TI has announced that the device will be discontinued, and a lifetime-buy period is in effect. NRND: Not recommended for new designs. Device is in production to support existing customers, but TI does not recommend using this part in a new design. PREVIEW: Device has been announced but is not in production. Samples may or may not be available. OBSOLETE: TI has discontinued the production of the device.

<sup>(2)</sup> Eco Plan - The planned eco-friendly classification: Pb-Free (RoHS), Pb-Free (RoHS Exempt), or Green (RoHS & no Sb/Br) - please check http://www.ti.com/productcontent for the latest availability information and additional product content details.

TBD: The Pb-Free/Green conversion plan has not been defined.

**Pb-Free (RoHS):** TI's terms "Lead-Free" or "Pb-Free" mean semiconductor products that are compatible with the current RoHS requirements for all 6 substances, including the requirement that lead not exceed 0.1% by weight in homogeneous materials. Where designed to be soldered at high temperatures, TI Pb-Free products are suitable for use in specified lead-free processes. **Pb-Free (RoHS Exempt):** This component has a RoHS exemption for either 1) lead-based flip-chip solder bumps used between the die and package, or 2) lead-based die adhesive used between the die and leadframe. The component is otherwise considered Pb-Free (RoHS compatible) as defined above.

Green (RoHS & no Sb/Br): TI defines "Green" to mean Pb-Free (RoHS compatible), and free of Bromine (Br) and Antimony (Sb) based flame retardants (Br or Sb do not exceed 0.1% by weight in homogeneous material)

<sup>(3)</sup> MSL, Peak Temp. -- The Moisture Sensitivity Level rating according to the JEDEC industry standard classifications, and peak solder temperature.

Important Information and Disclaimer: The information provided on this page represents TI's knowledge and belief as of the date that it is provided. TI bases its knowledge and belief on information provided by third parties, and makes no representation or warranty as to the accuracy of such information. Efforts are underway to better integrate information from third parties. TI has taken and continues to take reasonable steps to provide representative and accurate information but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals. TI and TI suppliers consider certain information to be proprietary, and thus CAS numbers and other limited information may not be available for release.

In no event shall TI's liability arising out of such information exceed the total purchase price of the TI part(s) at issue in this document sold by TI to Customer on an annual basis.


# PACKAGE MATERIALS INFORMATION

www.ti.com


Texas Instruments

### TAPE AND REEL INFORMATION





### QUADRANT ASSIGNMENTS FOR PIN 1 ORIENTATION IN TAPE




Device	Package Type	Package Drawing	Pins	SPQ	Reel Diameter (mm)	Reel Width W1 (mm)	A0 (mm)	B0 (mm)	K0 (mm)	P1 (mm)	W (mm)	Pin1 Quadrant
SN74LVT162244ADGGR	TSSOP	DGG	48	2000	330.0	24.4	8.6	15.8	1.8	12.0	24.0	Q1
SN74LVT162244ADGVR	TVSOP	DGV	48	2000	330.0	16.4	7.1	10.2	1.6	12.0	16.0	Q1
SN74LVT162244ADLR	SSOP	DL	48	1000	330.0	32.4	11.35	16.2	3.1	16.0	32.0	Q1
SN74LVT162244AGQLR	BGA MI CROSTA R JUNI OR	GQL	56	1000	330.0	16.4	4.8	7.3	1.45	8.0	16.0	Q1
SN74LVT162244AGRDR	BGA MI CROSTA R JUNI OR	GRD	54	1000	330.0	16.4	5.8	8.3	1.55	8.0	16.0	Q1
SN74LVT162244AZQLR	BGA MI CROSTA R JUNI OR	ZQL	56	1000	330.0	16.4	4.8	7.3	1.45	8.0	16.0	Q1
SN74LVT162244AZRDR	BGA MI CROSTA R JUNI OR	ZRD	54	1000	330.0	16.4	5.8	8.3	1.55	8.0	16.0	Q1

TEXAS INSTRUMENTS

www.ti.com

# PACKAGE MATERIALS INFORMATION

23-Jul-2011



*All dimensions are nominal							
Device	Package Type	Package Drawing	Pins	SPQ	Length (mm)	Width (mm)	Height (mm)
SN74LVT162244ADGGR	TSSOP	DGG	48	2000	346.0	346.0	41.0
SN74LVT162244ADGVR	TVSOP	DGV	48	2000	346.0	346.0	33.0
SN74LVT162244ADLR	SSOP	DL	48	1000	346.0	346.0	49.0
SN74LVT162244AGQLR	BGA MICROSTAR JUNIOR	GQL	56	1000	333.2	345.9	28.6
SN74LVT162244AGRDR	BGA MICROSTAR JUNIOR	GRD	54	1000	333.2	345.9	28.6
SN74LVT162244AZQLR	BGA MICROSTAR JUNIOR	ZQL	56	1000	333.2	345.9	28.6
SN74LVT162244AZRDR	BGA MICROSTAR JUNIOR	ZRD	54	1000	333.2	345.9	28.6

ZQL (R-PBGA-N56)

PLASTIC BALL GRID ARRAY



NOTES: A. All linear dimensions are in millimeters. Dimensioning and tolerancing per ASME Y14.5M-1994.


- B. This drawing is subject to change without notice.
- C. Falls within JEDEC MO-285 variation BA-2.
- D. This package is Pb-free. Refer to the 56 GQL package (drawing 4200583) for tin-lead (SnPb).

MicroStar Junior is a trademark of Texas Instruments



GRD (R-PBGA-N54)

PLASTIC BALL GRID ARRAY



NOTES: A. All linear dimensions are in millimeters.

B. This drawing is subject to change without notice.

Falls within JEDEC MO-205 variation DD.

D. This package is tin-lead (SnPb). Refer to the 54 ZRD package (drawing 4204760) for lead-free.



ZRD (R-PBGA-N54)

PLASTIC BALL GRID ARRAY



NOTES: A. All linear dimensions are in millimeters.

B. This drawing is subject to change without notice.

Falls within JEDEC MO-205 variation DD.

D. This package is lead-free. Refer to the 54 GRD package (drawing 4204759) for tin-lead (SnPb).



### **MECHANICAL DATA**

PLASTIC SMALL-OUTLINE

MPDS006C - FEBRUARY 1996 - REVISED AUGUST 2000

### DGV (R-PDSO-G\*\*)

24 PINS SHOWN



NOTES: A. All linear dimensions are in millimeters.

B. This drawing is subject to change without notice.

- C. Body dimensions do not include mold flash or protrusion, not to exceed 0,15 per side.
- D. Falls within JEDEC: 24/48 Pins MO-153

14/16/20/56 Pins – MO-194



GQL (R-PBGA-N56)

PLASTIC BALL GRID ARRAY



NOTES: A. All linear dimensions are in millimeters. Dimensioning and tolerancing per ASME Y14.5M-1994.

- B. This drawing is subject to change without notice.
- C. Falls within JEDEC MO-285 variation BA-2.
- D. This package is tin-lead (SnPb). Refer to the 56 ZQL package (drawing 4204437) for lead-free.



# **MECHANICAL DATA**

MSSO001C - JANUARY 1995 - REVISED DECEMBER 2001

#### PLASTIC SMALL-OUTLINE PACKAGE

48 PINS SHOWN

DL (R-PDSO-G\*\*)



NOTES: A. All linear dimensions are in inches (millimeters).

B. This drawing is subject to change without notice.

C. Body dimensions do not include mold flash or protrusion not to exceed 0.006 (0,15).

D. Falls within JEDEC MO-118



### **MECHANICAL DATA**

MTSS003D - JANUARY 1995 - REVISED JANUARY 1998

#### DGG (R-PDSO-G\*\*)

#### PLASTIC SMALL-OUTLINE PACKAGE

**48 PINS SHOWN** 



NOTES: A. All linear dimensions are in millimeters.

- B. This drawing is subject to change without notice.
- C. Body dimensions do not include mold protrusion not to exceed 0,15.
- D. Falls within JEDEC MO-153



#### **IMPORTANT NOTICE**

Texas Instruments Incorporated and its subsidiaries (TI) reserve the right to make corrections, modifications, enhancements, improvements, and other changes to its products and services at any time and to discontinue any product or service without notice. Customers should obtain the latest relevant information before placing orders and should verify that such information is current and complete. All products are sold subject to TI's terms and conditions of sale supplied at the time of order acknowledgment.

TI warrants performance of its hardware products to the specifications applicable at the time of sale in accordance with TI's standard warranty. Testing and other quality control techniques are used to the extent TI deems necessary to support this warranty. Except where mandated by government requirements, testing of all parameters of each product is not necessarily performed.

TI assumes no liability for applications assistance or customer product design. Customers are responsible for their products and applications using TI components. To minimize the risks associated with customer products and applications, customers should provide adequate design and operating safeguards.

TI does not warrant or represent that any license, either express or implied, is granted under any TI patent right, copyright, mask work right, or other TI intellectual property right relating to any combination, machine, or process in which TI products or services are used. Information published by TI regarding third-party products or services does not constitute a license from TI to use such products or services or a warranty or endorsement thereof. Use of such information may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

Reproduction of TI information in TI data books or data sheets is permissible only if reproduction is without alteration and is accompanied by all associated warranties, conditions, limitations, and notices. Reproduction of this information with alteration is an unfair and deceptive business practice. TI is not responsible or liable for such altered documentation. Information of third parties may be subject to additional restrictions.

Resale of TI products or services with statements different from or beyond the parameters stated by TI for that product or service voids all express and any implied warranties for the associated TI product or service and is an unfair and deceptive business practice. TI is not responsible or liable for any such statements.

TI products are not authorized for use in safety-critical applications (such as life support) where a failure of the TI product would reasonably be expected to cause severe personal injury or death, unless officers of the parties have executed an agreement specifically governing such use. Buyers represent that they have all necessary expertise in the safety and regulatory ramifications of their applications, and acknowledge and agree that they are solely responsible for all legal, regulatory and safety-related requirements concerning their products and any use of TI products in such safety-critical applications, notwithstanding any applications-related information or support that may be provided by TI. Further, Buyers must fully indemnify TI and its representatives against any damages arising out of the use of TI products in such safety-critical applications.

TI products are neither designed nor intended for use in military/aerospace applications or environments unless the TI products are specifically designated by TI as military-grade or "enhanced plastic." Only products designated by TI as military-grade meet military specifications. Buyers acknowledge and agree that any such use of TI products which TI has not designated as military-grade is solely at the Buyer's risk, and that they are solely responsible for compliance with all legal and regulatory requirements in connection with such use.

TI products are neither designed nor intended for use in automotive applications or environments unless the specific TI products are designated by TI as compliant with ISO/TS 16949 requirements. Buyers acknowledge and agree that, if they use any non-designated products in automotive applications, TI will not be responsible for any failure to meet such requirements.

Following are URLs where you can obtain information on other Texas Instruments products and application solutions:

Products		Applications	
Audio	www.ti.com/audio	Automotive and Transportation	www.ti.com/automotive
Amplifiers	amplifier.ti.com	Communications and Telecom	www.ti.com/communications
Data Converters	dataconverter.ti.com	Computers and Peripherals	www.ti.com/computers
DLP® Products	www.dlp.com	Consumer Electronics	www.ti.com/consumer-apps
DSP	dsp.ti.com	Energy and Lighting	www.ti.com/energy
Clocks and Timers	www.ti.com/clocks	Industrial	www.ti.com/industrial
Interface	interface.ti.com	Medical	www.ti.com/medical
Logic	logic.ti.com	Security	www.ti.com/security
Power Mgmt	power.ti.com	Space, Avionics and Defense	www.ti.com/space-avionics-defense
Microcontrollers	microcontroller.ti.com	Video and Imaging	www.ti.com/video
RFID	www.ti-rfid.com		
OMAP Mobile Processors	www.ti.com/omap		
Wireless Connectivity	www.ti.com/wirelessconnectivity		
	TI 505 0		

**TI E2E Community Home Page** 

e2e.ti.com

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265 Copyright © 2012, Texas Instruments Incorporated