



SPECIFICATION

宏致電子股份有限公司

桃園縣中壢市東園路13號

No.13, Dongyuan Rd., Zhongli City,

Taoyuan County 320, Taiwan (R.O.C.)

TEL: +886-3-463-2808

FAX: +886-3-463-1800

SPEC. NO.: PS-51495-xxxxx-xxx REVISION: E

PRODUCT NAME: 0.40mm PITCH LVDS CONNECTOR

PRODUCT NO: 51495、51496

| | | |
|---|---|---|
| PREPARED: Jia-Hong Xu DATE: 2023/07/20 | CHECKED: Yung-Huang Liu DATE: 2023/07/20 | APPROVED: Kuo-Hua Huang DATE: 2023/07/20 |
|---|---|---|

TITLE: 51495 LVDS CONNECTOR SPECIFICATION

RELEASE DATE:2023/07/20

REVISION:E

ECN No: ECN-013186

PAGE: 2 OF 20

| | | |
|----|---|----|
| 1 | REVISION HISTORY | 2 |
| 2 | SCOPE | 3 |
| 3 | APPLICABLE DOCUMENTS..... | 3 |
| 4 | REQUIREMENTS | 3 |
| 5 | PERFORMANCE | 4 |
| 6 | INFRARED REFLOW CONDITION | 9 |
| 7 | PRODUCT QUALIFICATION AND TEST SEQUENCE..... | 10 |
| 8 | RECOMMENDED METAL MASK..... | 12 |
| 9 | PRECAUTIONS FOR HANDLING CABLE CONNECTORS | 12 |
| 10 | INSTRUCTION MANUAL..... | 13 |

1 Revision History

| Rev. | ECN NO. | Revision Description | Prepared | Date |
|------|------------|--|----------|------------|
| A | ECN-000416 | NEW PRODUCT RELEASE | JH.XU | 2020/09/18 |
| B | ECN-000986 | SALT SPRAY(ONLY FOR GOLD PLATING) ADD 15u” GOLD PLATING | JH XU | 2020/11/11 |
| C | ECN-002576 | SALT SPRAY(ONLY FOR GOLD PLATING) ADD 10u” GOLD PLATING MATING FORCE AND UN-MATING FORCE ADD 20 PIN | JH.XU | 2021/03/17 |
| D | ECN-012279 | ADD AWG#33 cable specification | JH.XU | 2023/05/04 |
| E | ECN-013186 | ADD 51495-002/51496-MB type | JH.XU | 2023/07/20 |
| | | | | |
| | | | | |

TITLE: **51495 LVDS CONNECTOR SPECIFICATION**

RELEASE DATE:2023/07/20

REVISION:E

ECN No: ECN-013186

PAGE: 3 OF 20

2 SCOPE

This specification covers performance, tests and quality requirements for **0.40 mm pitch LVDS connector**.

3 APPLICABLE DOCUMENTS

EIA-364: ELECTRONICS INDUSTRIES ASSOCIATION

4 REQUIREMENTS

4.1 Design and Construction

- 4.1.1 Product shall be of design, construction and physical dimensions specified on applicable product drawing.
- 4.1.2 All materials conform to R.o.H.S. and the standard depends on TQ-WI-140101.

4.2 Materials and Finish

- 4.2.1 Terminal: High performance copper alloy (**Corson Alloy**)
 - Finish: (a) Contact Area: **Refer to the drawing**.
 - (b) Under plate: **Refer to the drawing**.
 - (c) Solder area: **Refer to the drawing**.
- 4.2.2 Housing Thermoplastic or Thermoplastic High Temp., UL94V-0
- 4.2.3 Shell: **Copper Alloy, Finish: Refer to the drawing**.

4.3 Ratings

- 4.3.1 Voltage: **100 Volts AC (per contact)**
- 4.3.2 Current: **0.1A AC/DC [AWG#44] (per contact)**
0.24A AC/DC [AWG#42] (per contact)
0.3A AC/DC [AWG#40] (per contact)
0.5A AC/DC [AWG#38] (per contact)
0.8A AC/DC [AWG#36] (per contact)
1.0A AC/DC [AWG#34] (per contact)
1.1A AC/DC [AWG#33] (per contact)
- 4.3.3 Operating Temperature : **-40°Cto +85°C**.
- 4.3.4 **Operating Humidity : 85% max**

4.4 Storage Conditions

- 4.4.1 Storage temperature : **-25°C~60°C**
- 4.4.2 Storage humidity: **85% max.(Non-condensing)**

TITLE: 51495 LVDS CONNECTOR SPECIFICATION

RELEASE DATE:2023/07/20

REVISION:E

ECN No: ECN-013186

PAGE: 4 OF 20

5 Performance

5.1. Test Requirements and Procedures Summary

| Item | Requirement | Standard |
|----------------------------------|---|---|
| Examination of Product | Product shall meet requirements of applicable product drawing and specification. | Visual, dimensional and functional per applicable quality inspection plan. |
| ELECTRICAL | | |
| Item | Requirement | Standard |
| Low Level Contact Resistance | Initial : 160mΩMAX.(AWG#33) 180mΩMAX.(AWG#34) 275mΩMAX.(AWG#36) 360mΩMAX.(AWG#38) 600mΩMAX.(AWG#40) 700mΩMAX.(AWG#42) 1080mΩMAX.(AWG#44) After test : ΔR 40mΩ MAX. Ground Shell Initial : 50mΩ MAX.. After testing : ΔR 40mΩ MAX. | According to EIA-364-23 Solder the receptacle connector to the test board and mate the plug connector together, than measure the contact resistance as shown in <u>Fig.1</u> by the four terminal methods. Apply the low level condition of 20 mV MAX. DC for the open circuit voltage and 100mA MAX. DC for the closed circuit current. |
| | Initial contains the following conductor resistance of a cable 100mm. 80mΩMAX.(AWG#33) 100mΩMAX.(AWG#34) 195mΩMAX.(AWG#36) 280mΩMAX.(AWG#38) 520mΩMAX.(AWG#40) 620mΩMAX.(AWG#42) 1000mΩMAX.(AWG#42) | |
| Insulation resistance | Initial: 1000MΩ MIN. After testing: 500 MΩ MIN. | According to EIA-364-21 Mate the plug and receptacle connectors together, and then apply 250 V DC between inner contact and the ground contact. |
| Dielectric Withstanding Voltage. | No discharge, flashover or breakdown. Current leakage: 1 mA max. | According to EIA-364-20 250 VAC Min. at sea level for 1 minute. |

TITLE: 51495 LVDS CONNECTOR SPECIFICATION

RELEASE DATE:2023/07/20

REVISION:E

ECN No: ECN-013186

PAGE: 5 OF 20

| | | |
|--------------------|-----------------------------------|---|
| | | Test between adjacent contacts of unmated connectors. |
| Temperature rising | Over ambient ΔT 30°C MAX. | According to EIA-364-70, Method1,Condition1 Mate connector: measure the temperature rise at rated current until temperature stable. The ambient condition is still air at 25°C The ambient condition is still air at 25°C |

MECHANICAL

| Item | Requirement | Standard |
|-----------------------------------|---|---|
| Mating force and Un-mating force. | See Table.1. | According to EIA-364-13 Method A Operation Speed : 25.4 ± 3 mm/minute.. Measure the force required to mate/un-mate connector. |
| Durability | Contact resistance : Shall meet Electrical Low Level Contact Resistance | According to EIA-364-09 Solder the receptacle connector to the test board, then place the board and plug on the push-on/pull-off machine, and repeat mating and un-mating 30cycles at a speed 25 ± 3 mm/min. Along the mating axis. |
| Contact retention force | Receptacle contact retention force: 0.2N MIN. | According to EIA-364-29 Place the connector on the push-on/pull off machine, then apply force on the contact head and push the contact along the direction opposite to the contact insertion at a speed of 25 ± 3 mm/min. Measure the force when the contact dislodges the |

TITLE: 51495 LVDS CONNECTOR SPECIFICATION

RELEASE DATE:2023/07/20

REVISION:E

ECN No: ECN-013186

PAGE: 6 OF 20

| | | |
|-----------------------|-----------------------|--|
| | | connector. |
| Cable retention force | 0.49 N Min.(Per Pin.) | <p>According to EIA-364-29</p> <p>Place the plug connector on the push-on/pull-off machine and then apply force on the cable along the direction at a speed 25 ± 3mm/min. Measure the force when the cable dislodged.</p> |
| Vibration | 1 μ s Max. | <p>According to EIA-364-28 Condition I</p> <p>The electrical load condition shall be 100 mA maximum for all contacts. Subject to a simple harmonic motion having amplitude of 0.76mm (1.52mm maximum total excursion) in frequency between the limits of 10 and 55 Hz. The entire frequency range, from 10 to 55 Hz and return to 10 Hz, shall be traversed in approximately 1 minute. This motion shall be applied for 2 hours in each of three mutually perpendicular directions.</p> |
| Shock (Mechanical) | 1 μ s Max. | <p>According to EIA-364-27, test condition A</p> <p>Subject mated connectors to 50 G's (peak value) half-sine shock pulses of 11 milliseconds duration. Three shocks in each direction shall be applied along the three mutually perpendicular axes of the test specimen (18 shocks). The electrical load condition shall be 100mA maximum for all contacts.</p> |

TITLE: 51495 LVDS CONNECTOR SPECIFICATION

RELEASE DATE:2023/07/20

REVISION:E

ECN No: ECN-013186

PAGE: 7 OF 20

| NO. OF Ckt. | Initial | | After 30 th Cycle | |
|-------------|---------------------|------------------------|------------------------------|-----------------------|
| | Mating Force (Max.) | Un-mating Force (Min.) | Mating Force (Max.) | Un-mating Force (Min) |
| 40 | 40N / 4.0Kgf | 4.0N / 0.4kgf | 40N / 4.0Kgf | 4.0N / 0.4kgf |
| 30 | 34N / 3.5Kgf | 3.0N / 0.3Kgf | 34N / 3.5Kgf | 3.0N / 0.3Kgf |
| 20 | 25N / 2.5Kgf | 2.0N / 0.2Kgf | 25N / 2.5Kgf | 2.0N / 0.2Kgf |

Table.1

| ENVIRONMENTAL | | |
|------------------------|--|---|
| Item | Requirement | Standard |
| Thermal shock | Contact resistance: Shall meet Low Level Contact Resistance. Insulation resistance: Shall meet Insulation resistance Dielectric withstanding voltage: Shall meet Dielectric Withstanding Voltage. Appearance: No abnormality | According to EIA-364-32 Mate module and subject to follow condition for 5 cycles. 1 cycles: -55 +0/-3 °C, 30 minutes +85 +3/-0 °C, 30 minutes |
| Temperature life | Contact resistance: Shall meet Low Level Contact Resistance. Contact retention force: Shall meet 5.2(MECHANICAL).3. Appearance: No abnormality | According to EIA-364-17 Solder the receptacle connector to the test board, then mate plug connector, and expose them to the following environment. Temperature: 85±2°C Duration: 250 hours. |
| Humidity(Steady state) | Contact resistance: Shall meet Low Level Contact Resistance. Insulation resistance: Shall meet Insulation resistance. Dielectric withstanding voltage: Shall meet Dielectric Withstanding Voltage. Appearance: No abnormality | According to EIA-364-31 Method II Solder the receptacle connector to the test board, then mate plug connector, and expose them to the following environment Temperature: 40±2°C Humidity:90~95%RH Duration: 240 hours |

TITLE: 51495 LVDS CONNECTOR SPECIFICATION

RELEASE DATE:2023/07/20

REVISION:E

ECN No: ECN-013186

PAGE: 8 OF 20

| | | |
|---------------------------------------|---|---|
| Humidity(Cycling) | <p>Contact resistance: Shall meet Low Level Contact Resistance. Insulation resistance: Shall meet Insulation resistance. Dielectric withstanding voltage: Shall meet Dielectric Withstanding Voltage. Appearance: No abnormality</p> | <p>According to EIA-364-31 Method III test, without Shock & Vibration section. Solder the receptacle connector to the test board, then mate plug connector, and expose them to the following environment Temperature: 25~65°C Humidity:90~98%RH Duration: 10cycles (240hours)</p> |
| Salt spray(Only for Gold Plating) | <p>Contact resistance: Shall meet Low Level Contact Resistance. Appearance: No abnormality</p> | <p>According to EIA-364-26 Subject mated connectors to 5% salt-solution concentration, 35°C (I) Gold plating 1u” for 8 hours (II) Gold plating 3 u” for 48 hours. (III) Gold plating 10 u” for 96 hours. (IV) Gold plating 15 u” for 96 hours.</p> |
| Resistance to Reflow Soldering Heat | <p>Contact resistance: Shall meet Low Level Contact Resistance. Appearance: No abnormality</p> | <p>According to EIA-364-56 Pre Heat : 150°C~180°C, 60~120sec. Heat : 230°C Min., 40sec Min. Peak Temp. : 260°CMax, 10sec Max. Reflow number cycle: 2 times</p> |
| Solder ability | <p>More than 75% of the dipped surface shall be evenly wet</p> | <p>According to EIA-364-52 And then into solder bath, Temperature at 245 ±5°C, for 4-5 sec.</p> |
| Hand Soldering Temperature Resistance | <p>Appearance: No damage</p> | <p>T ≥ 350°C, 3sec at least.</p> |

Note. Flowing Mixed Gas shell be conduct by customer request.

TITLE: 51495 LVDS CONNECTOR SPECIFICATION

RELEASE DATE:2023/07/20


REVISION:E

ECN No: ECN-013186

PAGE: 9 OF 20

6 INFRARED REFLOW CONDITION

6,1 Lead-Free Process



TITLE: 51495 LVDS CONNECTOR SPECIFICATION

RELEASE DATE:2023/07/20

REVISION:E

ECN No: ECN-013186

PAGE: 10 OF 20

7 PRODUCT QUALIFICATION AND TEST SEQUENCE

| Test or Examination | Test Group | | | | | | | | | | | |
|-------------------------------------|------------|-----|-------|-----|-----|-----|-----------------|-----|-----|-----|-----|-----|
| | 1 | 2 | 3 | 4 | 5 | 6 | 7 | 8 | 9 | 10 | 11 | 12 |
| Examination of Product | 1,10 | 1,5 | 1,4,7 | 1,9 | 1,5 | 1,9 | 1,11 | 1,5 | 1,3 | 1,3 | 1,3 | 1,3 |
| Low level Contact Resistance | 3,7 | | 2,5,8 | 2,6 | 2,4 | 2,6 | 2,6,8 | 2,4 | | | | |
| Insulation Resistance | | | | 3,7 | | 3,7 | 3,9 | | | | | |
| D. W. Voltage | | | | 4,8 | | 4,8 | 4,10 | | | | | |
| Temperature rising | | | | | | | | | | | 2 | |
| Mating Force | 2,6 | | | | | | | | | | | |
| Un-mating Force | 4,8 | | | | | | | | | | | |
| Durability | 5 | | | | | | 5 (10cycles) | | | | | |
| Contact Retention Force | | 2,4 | | | | | | | | | | |
| Cable Retention Force | 9 | | | | | | | | | | | |
| Vibration | | | 3 | | | | | | | | | |
| Shock | | | 6 | | | | | | | | | |
| Terminal Shock | | | | 5 | | | | | | | | |



TITLE: 51495 LVDS CONNECTOR SPECIFICATION

RELEASE DATE:2023/07/20

REVISION:E

ECN No: ECN-013186

PAGE: 11 OF 20

| | | | | | | | | | | | | |
|--|------|------|------|------|------|------|------|------|------|------|------|------|
| Temperature Life | | 3 | | | 3 | | | | | | | |
| Humidity (Steady State) | | | | | | 5 | | | | | | |
| Humidity(Cycling) | | | | | | | 7 | | | | | |
| Salt spray(Only for Gold Plating) | | | | | | | | 3 | | | | |
| Solder ability | | | | | | | | | 2 | | | |
| Soldering Heat Resistance | | | | | | | | | | 2 | | |
| Hand Soldering Temperature Resistance | | | | | | | | | | | | 2 |
| Sample Size | 4 | 20 | 4 | 4 | 4 | 4 | 4 | 4 | 2 | 2 | 2 | 2 |
| | Pcs. | Pos. | Pcs. | Pcs. | Pcs. | Pcs. | Pcs. | Pcs. | Pcs. | Pcs. | Pcs. | Pcs. |

TITLE: 51495 LVDS CONNECTOR SPECIFICATION

RELEASE DATE:2023/07/20

REVISION:E

ECN No: ECN-013186


PAGE: 12 OF 20

8 Recommended Metal Mask

Recommended thickness of METAL MASK: $t=0.10\text{mm}$.

Refer to drawing for the recommended metal mask opening dimension.

9 Precautions for Handling Cable Connectors



(Contact Resistance) = R_{AB}

Fig.1 Contact Resistance

TITLE: 51495 LVDS CONNECTOR SPECIFICATION

RELEASE DATE:2023/07/20

REVISION:E

ECN No: ECN-013186

PAGE: 13 OF 20

10 Instruction Manual

10.1 Connector Name, Part number.

| | Product Name | Part NO. |
|--------------------------|-------------------------------------|-----------------------------------|
| The cable side connector | 0,4mm Pitch WTB LVDS connector Plug | 51496-xxxxx-xxx 51496-Mxxx-xxx |
| The PCB side connector | 0.4mm Pitch LVDS. Rcpt. | 51495-xxxxx-xxx |

10.2 Names of each part of the connector.




Fig.2

TITLE: **51495 LVDS CONNECTOR SPECIFICATION**

RELEASE DATE:2023/07/20

REVISION:E

ECN No: ECN-013186

PAGE: 14 OF 20

10.3 Connector Insertion Manual
 10.3.1 Which direction to mate.

As shown in Fig.3, make sure place cable is soldered tail side.




Fig.3




Fig.4 Correct Connector Mating View

CAUTION

Do not mate the connector while cable is at soldered tail side.





Fig.5



TITLE: **51495 LVDS CONNECTOR SPECIFICATION**

RELEASE DATE:2023/07/20

REVISION:E

ECN No: ECN-013186

PAGE: 15 OF 20

10.4 How to mate

Open the Lock Bar first. Push the center of cable connector vertically until it clicks.

The clicking shows the mating completion. [Fig.6]

Close Lock Bar make sure Plug and Receptacle complete locked. [Fig.7]




Fig.6




Fig.7

CAUTION

·A support shall be designed and placed under PCB in order to prevent PCB from being deformed when cable connector is inserted with a pressing.

· The initial connector insertion angle allowance is given in Fig.8. Please set so that it becomes parallel without applying excessive force afterwards. Do not force to press cable connector when the insertion angle is out of this allowance angle.

Note 1. One side mating: Receptacle and plug mating slot side wall are touched on one end.

TITLE: **51495 LVDS CONNECTOR SPECIFICATION**

RELEASE DATE:2023/07/20

REVISION:E

ECN No: ECN-013186

PAGE: 16 OF 20





Fig.8 Insertion angle allowance

TITLE: **51495 LVDS CONNECTOR SPECIFICATION**

RELEASE DATE:2023/07/20

REVISION:E

ECN No: ECN-013186

PAGE: 17 OF 20

10.4.1 How to Withdraw Cable Connector by finger.

① Lift a lock cover finger hook outward on one end and repeat it again on opposite side to release lock cover. Make sure that the inner lock part is completely released. (See Fig.9)

② Hook **center** of the Lock Bar with finger and withdraw the connector. (See Fig.10)




Fig.9

TITLE: **51495 LVDS CONNECTOR SPECIFICATION**

RELEASE DATE:2023/07/20

REVISION:E

ECN No: ECN-013186

PAGE: 18 OF 20





Fig.10

CAUTION

- Do not un-mate a cable connector by pulling cable.
- When withdrawing the connector. We recommend that you pull the finger perpendicular to PCB.
- DO NOT WITHDRAWING FROM THE BOTTOM OF ONE SIDE(Fig.11)



DO NOT WITHDRAWING FROM THE BOTTOM OF ONE SIDE

Fig.11

TITLE: **51495 LVDS CONNECTOR SPECIFICATION**

RELEASE DATE:2023/07/20

REVISION:E

ECN No: ECN-013186

PAGE: 19 OF 20

10.4.2 Caution in Cable Connector Handling

- Handle the cable connector carefully in cable harnessing work so that pulling force is NOT applied to the cable attachment part of a cable connector.
- Be careful so that pulling force and/or repeated bending force is NOT applies to the cable attachment part of a cable connector.




Fig.12

- Do not pull cable that will apply excess force to it or it may damage or un-mate the connector.[Fig.13]
- Do not pull cable to un-mating connectors or it may damage receptacle.[Fig.14]

TITLE: **51495 LVDS CONNECTOR SPECIFICATION**

RELEASE DATE:2023/07/20

REVISION:E

ECN No: ECN-013186

PAGE: 20 OF 20




Fig.13-1




Fig.13-2




Fig.14-1




Fig.14-2