RoHS

SEOUL SEMICONDUCTOR

S1W0-5630XX9003-0000000-00004 - Mid-Power LED

Enabling the Best Im/W in Mid Power Range

Mid-Power LED - 5630 Series S1W0-5630XX9003-0000000-00004 (Cool, Neutral, Warm)



Product Brief

Description

- This White Colored surface-mount LED comes in standard package dimension. Package Size: 5.6x3.0x0.65mm
- It has a substrate made up of a molded plastic reflector sitting on top of a lead frame.
- The die is attached within the reflector cavity and the cavity is encapsulated by silicone.
- The package design coupled with careful selection of component materials allow these products to perform with high reliability.

Features and Benefits

- Market Standard 5630 Package Size •
- High Color Quality, CRI Min. 90
- ANSI & MacAdam 3 Step compliant
- **RoHS** compliant

Key Applications

- Interior lighting
- General lighting
- Indoor and outdoor displays
- Architectural / Decorative lighting

Deference Code	Calar	Nominal	Dent Number	CRI
Reference Code	Color	ССТ	Part Number	Min
	Cool White	5000K	S1W0-5630509003-00000000-00004	
	Neutral White	4000K	S1W0-5630409003-00000000-00004	-
STW9Q14D-E3		3500K	S1W0-5630359003-00000000-00004	90
	Warm White	3000K	S1W0-5630309003-00000000-00004	
		2700K	S1W0-5630279003-00000000-00004	

Table 1. Product Selection Table







Table of Contents

Inde	ex	
•	Product Brief	1
•	Table of Contents	2
•	Performance Characteristics	3
•	Characteristics Graph	5
•	Color Bin Structure	12
•	Mechanical Dimensions	15
•	Recommended Solder Pad	16
•	Reflow Soldering Characteristics	17
•	Emitter Tape & Reel Packaging	18
•	Product Nomenclature	20
•	Handling of Silicone Resin for LEDs	21
•	Precaution For Use	22
•	Company Information	25



Performance Characteristics

SEOUL

Table 2. Electro Optical Characteristics, I_F =65mA, T_j=25°C, RH30%

Min. CRI, Ra ^[4]	Nominal CCT [K] ^{[ŋ}	Min. Flux [Im] @65mA	Typ. Luminous Flux Φ _V ^[3] [lm] @65mA	Typ. Luminous Efficacy [lm/W] @65mA	Part Number
	5000	28.7	30.3	167.5	S1W0-5630509003- 00000000-00004
	4000	28.4	30.3	167.5	S1W0-5630409003- 00000000-00004
90	3500	28.1	29.7	164.2	S1W0-5630359003- 00000000-00004
	3000	26.6	28.7	159.1	S1W0-5630309003- 00000000-00004
	2700	26.6	28.1	155.6	S1W0-5630279003- 00000000-00004

- (1) Correlated color temperature is derived from the CIE 1931 chromaticity diagram
- (2) Seoul Semiconductor maintains a tolerance of ±7% on intensity and power measurements The luminous intensity IV was measured at the peak of the spatial pattern which may not be aligned with the mechanical axis of the LED package
- (3) The typical luminous flux table is only for reference
- (4) Solid angle 0.01sr (reference)

Performance Characteristics

SEOUL

Table 3. Characteristics, $I_F = 65 \text{mA}$, $T_j = 25^{\circ}\text{C}$, RH30%

Deremeter	Cumphiel	Value			110:4
Parameter	Symbol	Min.	Тур.	Max.	Unit
Forward Current	١ _F	-	65	-	mA
Forward Voltage	VF	-	2.78	2.80	V
CRI ^[3]	R _a	90	-	-	
Viewing Angle	2Θ _{1/2}	-	120	-	Deg.
Thermal resistance (J to S) ^[4]	Rθ _{J-S}	-	10	-	°C/W
ESD Sensitivity(HBM)	-		Class 3A JEDE	C JS-001-2017	

Table 4. Absolute Maximum Ratings

Parameter	Symbol	Value	Unit
Forward Current	I _F	200	mA
Power Dissipation	P _D	0.62	W
Junction Temperature	Т _і	125	٥C
Operating Temperature	T _{opr}	-40 ~ + 85	٥C
Storage Temperature	T _{stg}	-40 ~ + 100	٥C

- (1) Seoul Semiconductor maintains a tolerance of $\pm 7\%$ on intensity and power measurements
- (2) Correlated color temperature is derived from the CIE 1931 chromaticity diagram Color coordinate : ± 0.005 , CCT $\pm 5\%$ tolerance
- (3) Tolerance is ± 2.0 on CRI measurements
- (4) Thermal resistance is junction to solder
- (5) I_{FP} conditions with pulse width \leq 10ms and duty cycle \leq 10%
- (6) It is recommended to use it in the condition that the reliability is secured within the Max value.
- All measurements were made under the standardized environment of Seoul Semiconductor



Characteristics Graph

SEOUL

Fig 1. Color Spectrum, $T_j = 25^{\circ}C$, $I_F = 65mA$





Fig 2. Radiant Pattern, T_j= 25°C, I_F=65mA



S1W0-5630XX9003-0000000-00004 - Mid-Power LED

Characteristics Graph

SEOUL





Fig 3. Forward Voltage vs. Forward Current, T_j= 25°C


Fig 4. Forward Current vs. Relative Luminous Intensity, T_i = 25°C





S1W0-5630XX9003-0000000-00004 – Mid-Power LED

Characteristics Graph

SEOUL







S1W0-5630XX9003-0000000-00004 – Mid-Power LED

Characteristics Graph

SEOUL







Fig 7. Junction Temperature vs. Relative Forward Voltage, $I_F=65mA$



Characteristics Graph

SEOUL







Fig 8. Chromaticity Coordinate vs. Junction Temperature, I_F =65mA



Characteristics Graph

SEOUL









Performance Characteristics

SEOUL

Table 5. Bin Code Description, $T_j=25^{\circ}C$, $I_F=65mA$

PartNumber	Lumin	ous Flux @	5000K	Color	Typical Forward Voltage (V)		
Fart Number	Bin Code	Min.	Max.	Chromaticity Coordinate	Bin Code	Min.	Max.
	R5	27.1	28.7	Refer to Page. 12~14	Y1	2.7	2.8
S1W0- 5630XX9003-	S0	28.7	30.3		Y2	2.8	2.9
0000000- 00004	S5	30.3	31.9				

Table 6. Intensity Rank Distribution

Available Ranks


ССТ	CIE	IV Rank			
4700 ~ 5300K	С	R5	S0	S5	
3700 ~ 4200K	Е	R5	S0	S5	
3200 ~ 3700K	F	R5	S0	S5	
2900 ~ 3200K	G	R5	S0	S5	
2600 ~ 2900K	н	R5	S0	S5	

S1W0-5630XX9003-0000000-00004 - Mid-Power LED

Color Bin Structure

SEOUL

CIE Chromaticity Diagram (Cool white), $T_j=25$ °C, $I_F=65$ mA



5000K 3Step						
3C						
Center point	0.3447 : 0.3553					
Major Axis a	0.0081					
Minor Axis b	0.0035					
Ellipse Rotation Angle	60					


5000K 4Step					
4C					
Center point	0.3447 : 0.3553				
Major Axis a	0.0108				
Minor Axis b	0.0047				
Ellipse Rotation Angle	60				

С	A	l c	В	c	С	С	D
CIE X	CIE Y						
0.3376	0.3616	0.3463	0.3687	0.3452	0.3558	0.3371	0.3493
0.3371	0.3493	0.3452	0.3558	0.344	0.3428	0.3366	0.3369
0.3452	0.3558	0.3533	0.3624	0.3514	0.3487	0.344	0.3428
0.3463	0.3687	0.3551	0.376	0.3533	0.3624	0.3452	0.3558

Color Bin Structure

SEOUL

CIE Chromaticity Diagram (Cool white), $\,T_j {=} 25\,{}^\circ\!\!\mathbb{C},\,I_F {=} 65 mA$



4000K 3Step					
3E					
Center point	0.3818 : 0.3797				
Major Axis a	0.0094				
Minor Axis b	0.0040				
Ellipse Rotation Angle	53				

4000K 4Step					
4E					
Center point	0.3818 : 0.3797				
Major Axis a	0.0125				
Minor Axis b	0.0053				
Ellipse Rotation Angle	53				


E	A	E	В	E	c	E	D
CIE X	CIE Y						
0.3736	0.3874	0.3871	0.3959	0.3828	0.3803	0.3703	0.3726
0.3703	0.3726	0.3828	0.3803	0.3784	0.3647	0.367	0.3578
0.3828	0.3803	0.3952	0.388	0.3898	0.3716	0.3784	0.3647
0.3871	0.3959	0.4006	0.4044	0.3952	0.388	0.3828	0.3803

S1W0-5630XX9003-0000000-00004 - Mid-Power LED

Color Bin Structure

SEOUL

CIE Chromaticity Diagram (Cool white), $\,T_j\!=\!25\,^\circ\!\!\mathbb{C},\,I_F\!=\!65mA$



3500K 3Step 3 Step		3000K 3Step 3 Step		2700K 3Step 3 Step	
Center point	0.4073 : 0.3917	Center point	0.4338 : 0.4030	Center point	0.4578 : 0.4101
Major Axis a	0.0093	Major Axis a	0.0085	Major Axis a	0.0079
Minor Axis b	0.0041	Minor Axis b	0.0041	Minor Axis b	0.0041
Ellipse Rotation Angle	53	Ellipse Rotation Angle	53	Ellipse Rotation Angle	54


3500K 4Step		30001	K 4Step	2700K 4Step		
4 Step		4 Step		4 Step		
Center point	0.4073 : 0.3917	Center point	0.4338 : 0.4030	Center point	0.4578 : 0.4101	
Major Axis a	0.0124	Major Axis a	0.0113	Major Axis a	0.0105	
Minor Axis b	0.0055	Minor Axis b	0.0055	Minor Axis b	0.0055	
Ellipse Rotation Angle	53	Ellipse Rotation Angle	53	Ellipse Rotation Angle	54	

F	A	F	В	F	С	F	D
CIE X	CIE Y	CIE X	CIE Y	CIE X	CIE Y	CIE X	CIE Y
0.3996	0.4015	0.4146	0.4089	0.4082	0.392	0.3943	0.3853
0.3943	0.3853	0.4082	0.392	0.4017	0.3751	0.3889	0.369
0.4082	0.392	0.4223	0.399	0.4147	0.3814	0.4017	0.3751
0.4146	0.4089	0.4299	0.4165	0.4223	0.399	0.4082	0.392
G	A	G	В	G	c	G	D
CIE X	CIE Y	CIE X	CIE Y	CIE X	CIE Y	CIE X	CIE Y
0.4299	0.4165	0.443	0.4212	0.4345	0.4033	0.4223	0.399
0.4223	0.399	0.4345	0.4033	0.4259	0.3853	0.4147	0.3814
0.4345	0.4033	0.4468	0.4077	0.4373	0.3893	0.4259	0.3853
0.443	0.4212	0.4562	0.426	0.4468	0.4077	0.4345	0.4033
н	IA	н	В	н	с	н	D
CIE X	CIE Y	CIE X	CIE Y	CIE X	CIE Y	CIE X	CIE Y
0.4562	0.426	0.4687	0.4289	0.4585	0.4104	0.4468	0.4077
0.4468	0.4077	0.4585	0.4104	0.4483	0.3919	0.4373	0.3893
0.4585	0.4104	0.4703	0.4132	0.4593	0.3944	0.4483	0.3919
0.4687	0.4289	0.481	0.4319	0.4703	0.4132	0.4585	0.4104




S1W0-5630XX9003-0000000-00004 - Mid-Power LED

Mechanical Dimensions



Side View


Circuit



- (1) All dimensions are in millimeters
- (2) Scale: Not to scale
- (3) Undefined tolerance is $\pm 0.2 \text{mm}$



Recommended Solder Pad




- (1) All dimensions are in millimeters
- (2) Scale : Not to scale
- (3) This drawing without tolerances are for reference only
- (4) Undefined tolerance is $\pm 0.1 \text{mm}$
- (5) The appearance and specifications of the product may be changed for improvement without notice

S1W0-5630XX9003-0000000-00004 – Mid-Power LED

Reflow Soldering Characteristics

SEOUL



Profile Feature	Sn-Pb Eutectic Assembly	Pb-Free Assembly	
Average ramp-up rate (T_{s_max} to T_p)	3° C/second max.	3° C/second max.	
Preheat - Temperature Min (T _{s_min}) - Temperature Max (T _{s_max}) - Time (T _{s_min} to T _{s_max}) (t _s)	100 °C 150 °C 60-120 seconds	150 °C 200 °C 60-180 seconds	
Time maintained above: - Temperature (T _L) - Time (t _L)	183 °C 60-150 seconds	217 °C 60-150 seconds	
PeakTemperature (T _p)	215 ℃	260 ℃	
Time within 5°C of actual Peak Temperature (t _p)2	10-30 seconds	20-40 seconds	
Ramp-down Rate	6 °C/second max.	6 °C/second max.	
Time 25°C to PeakTemperature	6 minutes max.	8 minutes max.	


Caution :

- (1) Reflow soldering is recommended not to be done more than two times If more than 24hr has passed after first soldering, LEDs will be damaged
- (2) Repairs should not be done after the LEDs have been soldered When repair is unavoidable, suitable tools must be used
- (3) When soldering, do not put stress on the LEDs during heating
- (4) After soldering, do not warp the circuit board



S1W0-5630XX9003-0000000-00004 - Mid-Power LED

Emitter Tape & Reel Packaging




(Tolerance: $\pm 0.2, \ Unit:mm$)

- (1) Quantity : Max 4,500pcs/Reel
- (2) Cumulative tolerance : Cumulative tolerance/10 pitches to be $\pm 0.2 \text{mm}$
- (3) Adhesion strength of cover tape
- Adhesion strength to be 0.1-0.7N when the cover tape is torn off from the carrier tape at the angle of 10° to the carrier tape
- (4) Package : P/N, manufacturing data code No. and quantity to be indicated on a damp proof package





Emitter Tape & Reel Packaging



Product Nomenclature

SEOUL

Table 8. Part Numbering System : $X_1X_2X_3X_4X_5X_6X_7X_8$ -X₉

Part Number Code	Description	Part Number	Value
X ₁	Company	S	Seoul Semiconductor
X ₂	Level of Integration	1	Discrete LED
X ₃ X ₄	Technology	WO	General White
X ₅ X ₆ X ₇ X ₈	Dimension	5630	
X ₉ X ₁₀	ССТ	XX	
X ₁₁ X ₁₂	CRI	90	
X ₁₃ X ₁₄	Vf	03	
X ₁₅ X ₁₆ X ₁₇	Characteristic code Flux Rank	000	
X ₁₈ X ₁₉ X ₂₀	Characteristic code Vf Rank	000	
X ₂₁ X ₂₂	Characteristic code Color Step	00	
X ₂₃ X ₂₄	Туре	00	
X ₂₅ X ₂₆ X ₂₇	Internal code	004	





SEOUL


S1W0-5630XX9003-0000000-00004 – Mid-Power LED

Handling of Silicone Resin for LEDs

(1) During processing, mechanical stress on the surface should be minimized as much as possible. Sharp objects of all types should not be used to pierce the sealing compound.



(2) In general, LEDs should only be handled from the side. This also applies to LEDs without a silicone sealant, since the surface can also become scratched.



(3) When populating boards in SMT production, there are basically no restrictions regarding the form of the pick and place nozzle, except that mechanical pressure on the surface of the resin must be prevented. This is assured by choosing a pick and place nozzle which is larger than the LED's reflector area.

(4) Silicone differs from materials conventionally used for the manufacturing of LEDs. These conditions must be considered during the handling of such devices. Compared to standard encapsulants, silicone is generally softer, and the surface is more likely to attract dust.

As mentioned previously, the increased sensitivity to dust requires special care during processing. In cases where a minimal level of dirt and dust particles cannot be guaranteed, a suitable cleaning solution must be applied to the surface after the soldering of components.

(5) SSC suggests using isopropylalcohol for cleaning. In case other solvents are used, it must be assured that these solvents do not dissolve the package or resin. Ultrasonic cleaning is not recommended. Ultrasonic cleaning may cause damage to the LED.

(6) Please do not mold this product into another resin (epoxy, urethane, etc) and do not handle this. product with acid or sulfur material in sealed space.

Precaution for Use

(1) Storage

SEOUL

To avoid the moisture penetration, we recommend store in a dry box with a desiccant. The recommended storage temperature range is 40° C and a maximum humidity of RH90%.

(2) Use Precaution after Opening the Packaging

- Use SMT techniques properly when you solder the LED as separation of the lens may affect the light output efficiency.
 - Pay attention to the following:
 - a. Recommend conditions after opening the package
 - Sealing
 - Temperature : 30 $^\circ\!\!\mathbb{C}$ Humidity : less than RH60%
 - b. If the package has been opened more than 4 week (MSL_2a) or the color of the desiccant changes, components should be dried for 10-24hr at $65\pm5^\circ$ C
- (3) Do not apply mechanical force or excess vibration during the cooling process to normal temperature after soldering.
- (4) Do not rapidly cool device after soldering.
- (5) Components should not be mounted on warped (non coplanar) portion of PCB.
- (6) Radioactive exposure is not considered for the products listed here.
- (7) Gallium arsenide is used in some of the products listed in this publication.
 These products are dangerous if they are burned or shredded in the process of disposal.
 It is also dangerous to drink the liquid or inhale the gas generated by such products when chemically disposed.
- (8) This device should not be used in any type of fluid such as water, oil, organic solvent and etc. When washing is required, IPA (Isopropyl Alcohol) should be used.
- (9) When the LEDs are in operation the maximum current should be decided after measuring the package temperature.



SEOUL

- (10) The appearance and specifications of the product may be modified for improvement without notice.
- (11) Long time exposure of sunlight or occasional UV exposure will cause lens discoloration.
- (12) VOCs (Volatile organic compounds) emitted from materials used in the construction of fixtures can penetrate silicone encapsulants of LEDs and discolor when exposed to heat and photonic energy. The result can be a significant loss of light output from the fixture. Knowledge of the properties of the materials selected to be used in the construction of fixtures can help prevent these issues.
- (13) Attaching LEDs, do not use adhesives that outgas organic vapor.
- (14) The driving circuit must be designed to allow forward voltage only when it is ON or OFF. If the reverse voltage is applied to LED, migration can be generated resulting in LED damage.
- (15) Similar to most Solid state devices;

LEDs are sensitive to Electro-Static Discharge (ESD) and Electrical Over Stress (EOS). Below is a list of suggestions that Seoul Semiconductor purposes to minimize these effects.

a. ESD (Electro Static Discharge)

Electrostatic discharge (ESD) is defined as the release of static electricity when two objects come into contact. While most ESD events are considered harmless, it can be an expensive problem in many industrial environments during production and storage. The damage from ESD to an LEDs may cause the product to demonstrate unusual characteristics such as:

- Increase in reverse leakage current lowered turn-on voltage
- Abnormal emissions from the LED at low current

The following recommendations are suggested to help minimize the potential for an ESD event. One or more recommended work area suggestions:

- lonizing fan setup
- ESD table/shelf mat made of conductive materials
- ESD safe storage containers

One or more personnel suggestion options:

- Antistatic wrist-strap
- Antistatic material shoes
- Antistatic clothes

Environmental controls:

- Humidity control (ESD gets worse in a dry environment)



Precaution for Use

b. EOS (Electrical Over Stress)

Electrical Over-Stress (EOS) is defined as damage that may occur when an electronic device is subjected to a current or voltage that is beyond the maximum specification limits of the device. The effects from an EOS event can be noticed through product performance like:

- Changes to the performance of the LED package

(If the damage is around the bond pad area and since the package is completely encapsulated the package may turn on but flicker show severe performance degradation.)

- Changes to the light output of the luminaire from component failure
- Components on the board not operating at determined drive power

Failure of performance from entire fixture due to changes in circuit voltage and current across total circuit causing trickle down failures. It is impossible to predict the failure mode of every LED exposed to electrical overstress as the failure modes have been investigated to vary, but there are some common signs that will indicate an EOS event has occurred:

- Damage may be noticed to the bond wires (appearing similar to a blown fuse)
- Damage to the bond pads located on the emission surface of the LED package
- (shadowing can be noticed around the bond pads while viewing through a microscope)
- Anomalies noticed in the encapsulation and phosphoraround the bond wires.
- This damage usually appears due to the thermal stress produced during the EOS event.
- c. To help minimize the damage from an EOS event Seoul Semiconductor recommends utilizing:
 - A surge protection circuit
 - An appropriately rated over voltage protection device
 - A current limiting device



Company Information

Published by

SEOUL

Seoul Semiconductor © 2013 All Rights Reserved.

Company Information

Seoul Semiconductor (www.SeoulSemicon.com) manufacturers and packages a wide selection of light emitting diodes (LEDs) for the automotive, general illumination/lighting, Home appliance, signage and back lighting markets. The company is the world's fifth largest LED supplier, holding more than 10,000 patents globally, while offering a wide range of LED technology and production capacity in areas such as "nPola", "Acrich", the world's first commercially produced AC LED, and "Acrich MJT - Multi-Junction Technology" a proprietary family of high-voltage LEDs.

The company's broad product portfolio includes a wide array of package and device choices such as Acrich and Acirch2, high-brightness LEDs, mid-power LEDs, side-view LEDs, and through-hole type LEDs as well as custom modules, displays, and sensors.

Legal Disclaimer

Information in this document is provided in connection with Seoul Semiconductor products. With respect to any examples or hints given herein, any typical values stated herein and/or any information regarding the application of the device, Seoul Semiconductor hereby disclaims any and all warranties and liabilities of any kind, including without limitation, warranties of non-infringement of intellectual property rights of any third party. The appearance and specifications of the product can be changed to improve the quality and/or performance without notice.