

LH28F160S3HNS-TV

Flash Memory 16Mbit (2Mbitx8/1Mbitx16)

(Model Number: LHF16KTV) *Lead-free (Pb-free)*

Spec. Issue Date: October 25, 2004

Spec No: EL16X211



SPEC. No.	EL16	X 2	1 1
ISSUE:	Oct.	25,	2004

_					
Τ	\circ	•			
T	\circ	,			

SPECIFICATIONS
Product Type 16Mbit Flash Memory
LH28F160S3HNS-TV
Model No. (LHF16KTV)
*This specifications contains 60 pages including the cover and appendix. If you have any objections, please contact us before issuing purchasing order. CUSTOMERS ACCEPTANCE DATE:
BY: PRESENTED
BY: Y. HOTTA Dept. General Manager
REVIEWED BY: PREPARED BY: H. Takata 24. Lubota
Product Development Dept. I

Product Development Dept. I System-Flash Division Integrated Circuits Group SHARP CORPORATION

SHARP

LHF16KTV

- Handle this document carefully for it contains material protected by international copyright law. Any reproduction, full or in part, of this material is prohibited without the express written permission of the company.
- •When using the products covered herein, please observe the conditions written herein and the precautions outlined in the following paragraphs. In no event shall the company be liable for any damages resulting from failure to strictly adhere to these conditions and precautions.
 - (1) The products covered herein are designed and manufactured for the following application areas. When using the products covered herein for the equipment listed in Paragraph (2), even for the following application areas, be sure to observe the precautions given in Paragraph (2). Never use the products for the equipment listed in Paragraph (3).
 - Office electronics
 - Instrumentation and measuring equipment
 - Machine tools
 - Audiovisual equipment
 - Home appliance
 - •Communication equipment other than for trunk lines
 - (2) Those contemplating using the products covered herein for the following equipment which demands high reliability, should first contact a sales representative of the company and then accept responsibility for incorporating into the design fail-safe operation, redundancy, and other appropriate measures for ensuring reliability and safety of the equipment and the overall system.
 - Control and safety devices for airplanes, trains, automobiles, and other transportation equipment
 - Mainframe computers
 - Traffic control systems
 - Gas leak detectors and automatic cutoff devices
 - •Rescue and security equipment
 - •Other safety devices and safety equipment, etc.
 - (3) Do not use the products covered herein for the following equipment which demands extremely high performance in terms of functionality, reliability, or accuracy.
 - Aerospace equipment
 - Communications equipment for trunk lines
 - •Control equipment for the nuclear power industry
 - •Medical equipment related to life support, etc.
 - (4) Please direct all queries and comments regarding the interpretation of the above three Paragraphs to a sales representative of the company.
- Please direct all queries regarding the products covered herein to a sales representative of the company.



CONTENTS

PAGE	PAC	èΕ
1 INTRODUCTION 3	5 DESIGN CONSIDERATIONS	30
1.1 Product Overview3	5.1 Three-Line Output Control	30
	5.2 STS and Block Erase, Full Chip Erase, (Multi)	
2 PRINCIPLES OF OPERATION6	Word/Byte Write and Block Lock-Bit Configuration	or
2.1 Data Protection 7	Polling	30
	5.3 Power Supply Decoupling	30
3 BUS OPERATION 7	5.4 V _{PP} Trace on Printed Circuit Boards	30
3.1 Read 7	5.5 V _{CC} , V _{PP} , RP# Transitions	31
3.2 Output Disable 7	5.6 Power-Up/Down Protection	31
3.3 Standby7	5.7 Power Dissipation	31
3.4 Deep Power-Down7		
3.5 Read Identifier Codes Operation8	6 ELECTRICAL SPECIFICATIONS	32
3.6 Query Operation 8	6.1 Absolute Maximum Ratings	32
3.7 Write8	6.2 Operating Conditions	32
	6.2.1 Capacitance	32
4 COMMAND DEFINITIONS 8	6.2.2 AC Input/Output Test Conditions	33
4.1 Read Array Command11	6.2.3 DC Characteristics	34
4.2 Read Identifier Codes Command 11	6.2.4 AC Characteristics - Read-Only Operations .:	36
4.3 Read Status Register Command11	6.2.5 AC Characteristics - Write Operations	39
4.4 Clear Status Register Command11	6.2.6 Alternative CE#-Controlled Writes	42
4.5 Query Command	6.2.7 Reset Operations	45
4.5.1 Block Status Register 12	6.2.8 Block Erase, Full Chip Erase, (Multi)	
4.5.2 CFI Query Identification String 13	Word/Byte Write and Block Lock-Bit	
4.5.3 System Interface Information	Configuration Performance	46
4.5.4 Device Geometry Definition		
4.5.5 SCS OEM Specific Extended Query Table 14	7 ADDITIONAL INFORMATION	
4.6 Block Erase Command	7.1 Ordering Information	48
4.7 Full Chip Erase Command		
4.8 Word/Byte Write Command	8 PACKAGE AND PACKING SPECIFICATION	49
4.9 Multi Word/Byte Write Command		
4.10 Block Erase Suspend Command		
4.11 (Multi) Word/Byte Write Suspend Command 17		
4.12 Set Block Lock-Bit Command		
4.13 Clear Block Lock-Bits Command		
4.14 STS Configuration Command		



LH28F160S3HNS-TV 16M-BIT (2MBx8/1MBx16) Smart 3 Flash MEMORY

- Smart 3 Technology
 - 2.7V or 3.3V V_{CC}
 - 2.7V, 3.3V or 5V V_{PP}
- Common Flash Interface (CFI)
 - Universal & Upgradable Interface
- Scalable Command Set (SCS)
- **■** High Speed Write Performance
 - 32 Bytes x 2 plane Page Buffer
 - 2.7 µs/Byte Write Transfer Rate
- **■** High Speed Read Performance
 - 100ns(3.3V±0.3V), 120ns(2.7V-3.6V)
- **■** Operating Temperature
 - -40°C to +85°C
- **■** Enhanced Automated Suspend Options
 - Write Suspend to Read
 - Block Erase Suspend to Write
 - Block Erase Suspend to Read
- High-Density Symmetrically-Blocked Architecture
 - Thirty-two 64K-byte Erasable Blocks
- SRAM-Compatible Write Interface
- User-Configurable x8 or x16 Operation

- Enhanced Data Protection Features
 - Absolute Protection with V_{PP}=GND
 - Flexible Block Locking
 - Erase/Write Lockout during Power Transitions
- **■** Extended Cycling Capability
 - 100,000 Block Erase Cycles
 - 3.2 Million Block Erase Cycles/Chip
- **■** Low Power Management
 - Deep Power-Down Mode
 - Automatic Power Savings Mode
 Decreases I_{CC} in Static Mode
- Automated Write and Erase
 - Command User Interface
 - Status Register
- Industry-Standard Packaging
 - 56-Lead SSOP
- ETOX^{TM*} V Nonvolatile Flash Technology
- CMOS Process (P-type silicon substrate)
- Not designed or rated as radiation hardened

SHARP's LH28F160S3HNS-TV Flash memory with Smart 3 technology is a high-density, low-cost, nonvolatile, read/write storage solution for a wide range of applications. Its symmetrically-blocked architecture, flexible voltage and extended cycling provide for highly flexible component suitable for resident flash arrays, SIMMs and memory cards. Its enhanced suspend capabilities provide for an ideal solution for code + data storage applications. For secure code storage applications, such as networking, where code is either directly executed out of flash or downloaded to DRAM, the LH28F160S3HNS-TV offers three levels of protection: absolute protection with $V_{\rm PP}$ at GND, selective hardware block locking, or flexible software block locking. These alternatives give designers ultimate control of their code security needs.

The LH28F160S3HNS-TV is conformed to the flash Scalable Command Set (SCS) and the Common Flash Interface (CFI) specification which enable universal and upgradable interface, enable the highest system/device data transfer rates and minimize device and system-level implementation costs.

The LH28F160S3HNS-TV is manufactured on SHARP's 0.35μm ETOX^{TM*} V process technology. It come in industry-standard package: the 56-Lead SSOP ideal for board constrained applications.

*ETOX is a trademark of Intel Corporation.



1 INTRODUCTION

This datasheet contains LH28F160S3HNS-TV specifications. Section 1 provides a flash memory overview. Sections 2, 3, 4, and 5 describe the memory organization and functionality. Section 6 covers electrical specifications.

1.1 Product Overview

The LH28F160S3HNS-TV is a high-performance 16M-bit Smart 3 Flash memory organized as 2MBx8/1MBx16. The 2MB of data is arranged in thirty-two 64K-byte blocks which are individually erasable, lockable, and unlockable in-system. The memory map is shown in Figure 3.

Smart 3 technology provides a choice of V_{CC} and V_{PP} combinations, as shown in Table 1, to meet system performance and power expectations. 2.7V V_{CC} consumes approximately one-fifth the power of 5V V_{CC} . V_{PP} at 2.7V, 3.3V and 5V eliminates the need for a separate 12V converter, while V_{PP} =5V maximizes erase and write performance. In addition to flexible erase and program voltages, the dedicated V_{PP} pin gives complete data protection when $V_{PP} \le V_{PPLK}$.

Table 1. V_{CC} and V_{PP} Voltage Combinations Offered by Smart 3 Technology

V _{CC} Voltage	V _{PP} Voltage
2.7V	2.7V, 3.3V, 5V
3.3V	3.3V, 5V

Internal V_{CC} and V_{PP} detection Circuitry automatically configures the device for optimized read and write operations.

A Command User Interface (CUI) serves as the interface between the system processor and internal operation of the device. A valid command sequence written to the CUI initiates device automation. An internal Write State Machine (WSM) automatically executes the algorithms and timings necessary for block erase, full chip erase, (multi) word/byte write and block lock-bit configuration operations.

A block erase operation erases one of the device's 64K-byte blocks typically within 0.41s (3.3V V_{CC} , 5V V_{PP}) independent of other blocks. Each block can be independently erased 100,000 times (3.2 million block erases per device). Block erase suspend mode allows system software to suspend block erase to read or write data from any other block.

A word/byte write is performed in byte increments typically within 12.95 μ s (3.3V V_{CC}, 5V V_{PP}). A multi word/byte write has high speed write performance of 2.7 μ s/byte (3.3V V_{CC}, 5V V_{PP}). (Multi) Word/byte

write suspend mode enables the system to read data or execute code from any other flash memory array location.

Individual block locking uses a combination of bits and WP#, Thirty-two block lock-bits, to lock and unlock blocks. Block lock-bits gate block erase, full chip erase and (multi) word/byte write operations. Block lock-bit configuration operations (Set Block Lock-Bit and Clear Block Lock-Bits commands) set and cleared block lock-bits.

The status register indicates when the WSM's block erase, full chip erase, (multi) word/byte write or block lock-bit configuration operation is finished.

The STS output gives an additional indicator of WSM activity by providing both a hardware signal of status (versus software polling) and status masking (interrupt masking for background block erase, for example). Status polling using STS minimizes both CPU overhead and system power consumption. STS pin can be configured to different states using the Configuration command. The STS pin defaults to RY/BY# operation. When low, STS indicates that the WSM is performing a block erase, full chip erase, (multi) word/byte write or block lock-bit configuration. STS-High Z indicates that the WSM is ready for a new command, block erase is suspended and (multi) word/byte write are inactive, (multi) word/byte write are suspended, or the device is in deep power-down mode. The other 3 alternate configurations are all pulse mode for use as a system interrupt.

The access time is 100ns (t_{AVQV}) over the extended temperature range (-40°C to +85°C) and V_{CC} supply voltage range of 3.0V-3.6V. At lower V_{CC} voltage, the access time is 120ns (2.7V-3.6V).

The Automatic Power Savings (APS) feature substantially reduces active current when the device is in static mode (addresses not switching). In APS mode, the typical I_{CCR} current is 3 mA at 3.3V V_{CC} .

When either $CE_0^{\#}$ or $CE_1^{\#}$, and RP# pins are at V_{CC} , the I_{CC} CMOS standby mode is enabled. When the RP# pin is at GND, deep power-down mode is enabled which minimizes power consumption and provides write protection during reset. A reset time (t_{PHQV}) is required from RP# switching high until outputs are valid. Likewise, the device has a wake time (t_{PHEL}) from RP#-high until writes to the CUI are recognized. With RP# at GND, the WSM is reset and the status register is cleared.

The device is available in 56-Lead SSOP (Shrink Small Outline Package). Pinout is shown in Figure 2.






Figure 1. Block Diagram




Figure 2. SSOP 56-Lead Pinout



		Table 2. Pin Descriptions
Symbol	Type	Name and Function
A ₀ -A ₂₀	INPUT	ADDRESS INPUTS: Inputs for addresses during read and write operations. Addresses are internally latched during a write cycle. Ao: Byte Select Address. Not used in x16 mode(can be floated). A1-A4: Column Address. Selects 1 of 16 bit lines. A5-A15: Row Address. Selects 1 of 2048 word lines. A16-A20: Block Address.
DQ ₀ -DQ ₁₅	INPUT/ OUTPUT	DATA INPUT/OUTPUTS: $ DQ_0\text{-}DQ_7\text{:Inputs data and commands during CUI write cycles; outputs data during memory array, status register, query, and identifier code read cycles. Data pins float to high-impedance when the chip is deselected or outputs are disabled. Data is internally latched during a write cycle. DQ_8\text{-}DQ_{15}:Inputs data during CUI write cycles in x16 mode; outputs data during memory array read cycles in x16 mode; not used for status register, query and identifier code read mode. Data pins float to high-impedance when the chip is deselected, outputs are disabled, or in x8 mode(Byte#=V_IL). Data is internally latched during a write cycle. $
CE ₀ #, CE ₁ #	INPUT	CHIP ENABLE: Activates the device's control logic, input buffers decoders, and sense amplifiers. Either CE ₀ # or CE ₁ # V _{IH} deselects the device and reduces power consumption to standby levels. Both CE ₀ # and CE ₁ # must be V _{II} to select the devices.
RP#	INPUT	RESET/DEEP POWER-DOWN: Puts the device in deep power-down mode and resets internal automation. RP# V _{IH} enables normal operation. When driven V _{IL} , RP# inhibits write operations which provides data protection during power transitions. Exit from deep power-down sets the device to read array mode.
OE#	INPUT	OUTPUT ENABLE: Gates the device's outputs during a read cycle.
WE#	INPUT	WRITE ENABLE: Controls writes to the CUI and array blocks. Addresses and data are latched on the rising edge of the WE# pulse.
STS	OPEN DRAIN OUTPUT	STS (RY/BY#): Indicates the status of the internal WSM. When configured in level mode (default mode), it acts as a RY/BY# pin. When low, the WSM is performing an internal operation (block erase, full chip erase, (multi) word/byte write or block lock-bit configuration). STS High Z indicates that the WSM is ready for new commands, block erase is suspended, and (multi) word/byte write is inactive, (multi) word/byte write is suspended or the device is in deep power-down mode. For alternate configurations of the STATUS pin, see the Configuration command.
WP#	INPUT	WRITE PROTECT: Master control for block locking. When V _{IL} , Locked blocks can not be erased and programmed, and block lock-bits can not be set and reset.
BYTE#	INPUT	BYTE ENABLE: BYTE# V_{IL} places device in x8 mode. All data is then input or output on DQ ₀₋₇ , and DQ ₈₋₁₅ float. BYTE# V_{IH} places the device in x16 mode, and turns off the A ₀ input buffer.
V _{PP}	SUPPLY	BLOCK ERASE, FULL CHIP ERASE, (MULTI) WORD/BYTE WRITE, BLOCK LOCK-BIT CONFIGURATION POWER SUPPLY: For erasing array blocks, writing bytes or configuring block lock-bits. With $V_{PP} \le V_{PPLK}$, memory contents cannot be altered. Block erase, full chip erase, (multi) word/byte write and block lock-bit configuration with an invalid V_{PP} (see DC Characteristics) produce spurious results and should not be attempted.
V _{CC}	SUPPLY	DEVICE POWER SUPPLY: Internal detection configures the device for 2.7V or 3.3V operation. To switch from one voltage to another, ramp V_{CC} down to GND and then ramp V_{CC} to the new voltage. Do not float any power pins. With $V_{CC} \le V_{LKO}$, all write attempts to the flash memory are inhibited. Device operations at invalid V_{CC} voltage (see DC Characteristics) produce spurious results and should not be attempted.
GND	SUPPLY	GROUND: Do not float any ground pins.
NC		NO CONNECT: Lead is not internal connected; it may be driven or floated.



2 PRINCIPLES OF OPERATION

The LH28F160S3HNS-TV Flash memory includes an on-chip WSM to manage block erase, full chip erase, (multi) word/byte write and block lock-bit configuration functions. It allows for: 100% TTL-level control inputs, fixed power supplies during block erase, full chip erase, (multi) word/byte write and block lock-bit configuration, and minimal processor overhead with RAM-Like interface timings.

After initial device power-up or return from deep power-down mode (see Bus Operations), the device defaults to read array mode. Manipulation of external memory control pins allow array read, standby, and output disable operations.

Status register, query structure and identifier codes can be accessed through the CUI independent of the V_{PP} voltage. High voltage on V_{PP} enables successful block erase, full chip erase, (multi) word/byte write and block lock-bit configuration. All functions associated with altering memory contents—block erase, full chip erase, (multi) word/byte write and block lock-bit configuration, status, query and identifier codes—are accessed via the CUI and verified through the status register.

Commands are written using standard microprocessor write timings. The CUI contents serve as input to the WSM, which controls the block erase, full chip erase, (multi) word/byte write and block lock-bit configuration. The internal algorithms are regulated by the WSM, including pulse repetition, internal verification, and margining of data. Addresses and data are internally latch during write cycles. Writing the appropriate command outputs array data, accesses the identifier codes, outputs query structure or outputs status register data.

Interface software that initiates and polls progress of block erase, full chip erase, (multi) word/byte write and block lock-bit configuration can be stored in any block. This code is copied to and executed from system RAM during flash memory updates. After successful completion, reads are again possible via the Read Array command. Block erase suspend allows system software to suspend a block erase to read or write data from any other block. Write suspend allows system software to suspend a (multi) word/byte write to read data from any other flash memory array location.

1FFFFF		
1F0000	64K-byte Block	31
1EFFFF 1E0000	64K-byte Block	30
1DFFFF 1D0000	64K-byte Block	29
1CFFFF	64K-byte Block	28
1C0000 1BFFFF	64K-byte Block	27
1B0000 1AFFFF	64K-byte Block	26
1A0000 19FFFF	64K-byte Block	25
190000 18FFFF	64K-byte Block	24
180000 17FFFF	64K-byte Block	23
170000 16FFFF	64K-byte Block	22
160000 15FFFF	<u> </u>	21
150000 14FFFF	64K-byte Block	
140000 13FFFF	64K-byte Block	20
130000 12FFFF	64K-byte Block	19
120000 11FFFF	64K-byte Block	18
110000	64K-byte Block	17
10FFFF 100000	64K-byte Block	16
0FFFFF 0F0000	64K-byte Block	15
0EFFFF 0E0000	64K-byte Block	14
0DFFFF 0D0000	64K-byte Block	13
0CFFFF 0C0000	64K-byte Block	12
0BFFFF 0B0000	64K-byte Block	11
0AFFFF 0A0000	64K-byte Block	10
09FFFF	64K-byte Block	9
090000 08FFFF	64K-byte Block	8
080000 07FFF	64K-byte Block	7
070000 06FFFF	64K-byte Block	6
060000 05FFFF	64K-byte Block	5
050000 04FFFF	64K-byte Block	4
040000 03FFFF	64K-byte Block	3
030000 02FFFF	64K-byte Block	2
020000 01FFFF	,	1
010000 00FFFF	64K-byte Block	
000000	64K-byte Block	0

Figure 3. Memory Map



2.1 Data Protection

Depending on the application, the system designer may choose to make the V_{PP} power supply switchable (available only when block erase, full chip erase, (multi) word/byte write and block lock-bit configuration are required) or hardwired to $V_{PPH1/2/3}$. The device accommodates either design practice and encourages optimization of the processor-memory interface.

When $V_{PP} \le V_{PPLK}$, memory contents cannot be altered. The CUI, with multi-step block erase, full chip erase, (multi) word/byte write and block lock-bit configuration command sequences, provides protection from unwanted operations even when high voltage is applied to V_{PP} . All write functions are disabled when V_{CC} is below the write lockout voltage V_{LKO} or when RP# is at V_{IL} . The device's block locking capability provides additional protection from inadvertent code or data alteration by gating block erase, full chip erase and (multi) word/byte write operations.

3 BUS OPERATION

The local CPU reads and writes flash memory insystem. All bus cycles to or from the flash memory conform to standard microprocessor bus cycles.

3.1 Read

Information can be read from any block, identifier codes, query structure, or status register independent of the V_{PP} voltage. RP# must be at V_{IH} .

The first task is to write the appropriate read mode command (Read Array, Read Identifier Codes, Query or Read Status Register) to the CUI. Upon initial device power-up or after exit from deep power-down mode, the device automatically resets to read array mode. Five control pins dictate the data flow in and out of the component: CE# (CE $_0$ #, CE $_1$ #), OE#, WE#, RP# and WP#. CE $_0$ #, CE $_1$ # and OE# must be driven active to obtain data at the outputs. CE $_0$ #, CE $_1$ # is the device selection control, and when active enables the selected memory device. OE# is the data output (DQ $_0$ -DQ $_1$ 5) control and when active drives the selected memory data onto the I/O bus. WE# and RP# must be at V $_{IH}$. Figure 17, 18 illustrates a read cycle.

3.2 Output Disable

With OE# at a logic-high level (V_{IH}), the device outputs are disabled. Output pins DQ₀-DQ₁₅ are placed in a high-impedance state.

3.3 Standby

Either CE₀# or CE₁# at a logic-high level (V_{IH}) places the device in standby mode which substantially reduces device power consumption. DQ₀-DQ₁₅ outputs are placed in a high-impedance state independent of OE#. If deselected during block erase, full chip erase, (multi) word/byte write and block lock-bit configuration, the device continues functioning, and consuming active power until the operation completes.

3.4 Deep Power-Down

RP# at V_{II} initiates the deep power-down mode.

In read modes, RP#-low deselects the memory, places output drivers in a high-impedance state and turns off all internal circuits. RP# must be held low for a minimum of 100 ns. Time t_{PHQV} is required after return from power-down until initial memory access outputs are valid. After this wake-up interval, normal operation is restored. The CUI is reset to read array mode and status register is set to 80H.

During block erase, full chip erase, (multi) word/byte write or block lock-bit configuration modes, RP#-low will abort the operation. STS remains low until the reset operation is complete. Memory contents being altered are no longer valid; the data may be partially erased or written. Time $t_{\rm PHWL}$ is required after RP# goes to logic-high (V $_{\rm IH}$) before another command can be written.

As with any automated device, it is important to assert RP# during system reset. When the system comes out of reset, it expects to read from the flash memory. Automated flash memories provide status information when accessed during block erase, full chip erase, (multi) word/byte write and block lock-bit configuration. If a CPU reset occurs with no flash memory reset, proper CPU initialization may not occur because the flash memory may be providing status information instead of array data. SHARP's flash memories allow proper CPU initialization following a system reset through the use of the RP# input. In this application, RP# is controlled by the same RESET# signal that resets the system CPU.



3.5 Read Identifier Codes Operation

The read identifier codes operation outputs the manufacturer code, device code, block status codes for each block (see Figure 4). Using the manufacturer and device codes, the system CPU can automatically match the device with its proper algorithms. The block status codes identify locked or unlocked block setting and erase completed or erase uncompleted condition.




Figure 4. Device Identifier Code Memory Map

3.6 Query Operation

The query operation outputs the query structure. Query database is stored in the 48Byte ROM. Query structure allows system software to gain critical information for controlling the flash component. Query structure are always presented on the lowest-order data output (DQ_0-DQ_7) only.

3.7 Write

Writing commands to the CUI enable reading of device data and identifier codes. They also control inspection and clearing of the status register. When $V_{\rm CC}=V_{\rm CC1/2}$ and $V_{\rm PP}=V_{\rm PPH1/2/3}$, the CUI additionally controls block erase, full chip erase, (multi) word/byte write and block lock-bit configuration.

The Block Erase command requires appropriate command data and an address within the block to be erased. The Word/byte Write command requires the command and address of the location to be written. Set Block Lock-Bit command requires the command and block address within the device (Block Lock) to be locked. The Clear Block Lock-Bits command requires the command and address within the device.

The CUI does not occupy an addressable memory location. It is written when WE# and CE# are active. The address and data needed to execute a command are latched on the rising edge of WE# or CE# (whichever goes high first). Standard microprocessor write timings are used. Figures 19 and 20 illustrate WE# and CE#-controlled write operations.

4 COMMAND DEFINITIONS

When the V_{PP} voltage $\leq V_{PPLK}$, Read operations from the status register, identifier codes, query, or blocks are enabled. Placing $V_{PPH1/2/3}$ on V_{PP} enables successful block erase, full chip erase, (multi) word/byte write and block lock-bit configuration operations.

Device operations are selected by writing specific commands into the CUI. Table 4 defines these commands.

Table 3. Bus Operations(BYTE#=V...)

rable 3. Dus Operations(DTTE#=VIH)										
Mode	Notes	RP#	CE ₀ #	CE ₁ #	OE#	WE#	Address	V _{PP}	DQ ₀₋₁₅	STS
Read	1,2,3,9	V_{IH}	VII	VII	V _{II}	V _{IH}	X		D _{OUT}	Χ
Output Disable	3	V _{IH}	Vil	Vil	V _{IH}	V _{IH}	Х	Χ	High Z	Х
Standby	3	V _{IH}	V _{IH} V _{IH} V _{II}	V _{IH} V _{IL} V _{IH}	X	X	х	X	High Z	Х
Deep Power-Down	4	V _{II}	X	X	Х	Х	Х	Х	High Z	High Z
Read Identifier Codes	9	V _{IH}	V _{IL}	V _{IL}	V _{IL}	V _{IH}	See Figure 4	Х	Note 5	High Z
Query	9	V_{IH}	V _{IL}	V _{IL}	V _{IL}	V _{IH}	See Table 7~11	Χ	Note 6	High Z
Write	3,7,8,9	V _{IH}	V _{IL}	V _{IL}	V _{IH}	V _{II}	Х	Χ	D _{IN}	Χ

Table 3.1. Bus Operations(BYTE#=V_{II})

				ouc opc.	~	· · · —	IL/			
Mode	Notes	RP#	CE ₀ #	CE ₁ #	OE#	WE#	Address	V_{PP}	DQ ₀₋₇	STS
Read	1,2,3,9	V_{IH}	VII	VII	V _{II}	V _{IH}	X	Χ	D _{OUT}	X
Output Disable	3	V _{IH}	V _{II}	V _{II}	V _{IH}	V _{IH}	X	Χ	High Z	X
Standby	3	V _{IH}	V _{IH} V _{IH} V _{II}	V _{IH} V _{IL} V _{IH}	X	X	X	Х	High Z	Х
Deep Power-Down	4	V _{II}	X	X	Х	Х	X	Х	High Z	High Z
Read Identifier Codes	9	V _{IH}	V _{IL}	V _{IL}	V _{IL}	V _{IH}	See Figure 4	Х	Note 5	High Z
Query	9	V _{IH}	V _{IL}	V _{IL}	V _{IL}	V _{IH}	See Table 7~11	Х	Note 6	High Z
Write	3,7,8,9	V_{IH}	V _{IL}	V_{IL}	V _{IH}	V _{IL}	X	Χ	D _{IN}	Х

NOTES:

- Refer to DC Characteristics. When V_{PP}≤V_{PPLK}, memory contents can be read, but not altered.
 X can be V_{IL} or V_{IH} for control pins and addresses, and V_{PPLK} or V_{PPH1/2/3} for V_{PP}. See DC Characteristics for V_{PPLK} and V_{PPH1/2/3} voltages.
- 3. STS is V_{OI} (if configured to RY/BY# mode) when the WSM is executing internal block erase, full chip erase, (multi) word/byte write or block lock-bit configuration algorithms. It is floated during when the WSM is not busy, in block erase suspend mode with (multi) word/byte write inactive, (multi) word/byte write suspend mode, or deep power-down mode.
- 4. RP# at GND±0.2V ensures the lowest deep power-down current.
- 5. See Section 4.2 for read identifier code data.
- 6. See Section 4.5 for query data.
- 7. Command writes involving block erase, full chip erase, (multi) word/byte write or block lock-bit configuration are reliably executed when $V_{PP}=V_{PPH1/2/3}$ and $V_{CC}=V_{CC1/2}$. 8. Refer to Table 4 for valid D_{IN} during a write operation. 9. Don't use the timing both OE# and WE# are V_{IL} .



Table 4. Command Definitions ⁽¹⁰⁾								
	Bus Cycles	Notes		st Bus Cy			ond Bus C	Cycle
Command	Req'd		Oper ⁽¹⁾	Addr ⁽²⁾	Data ⁽³⁾	Oper ⁽¹⁾	Addr ⁽²⁾	Data ⁽³⁾
Read Array/Reset	1		Write	X	FFH			
Read Identifier Codes	≥2	4	Write	X	90H	Read	IA	ID
Query	≥2		Write	X	98H	Read	QA	QD
Read Status Register	2		Write	Х	70H	Read	Х	SRD
Clear Status Register	1		Write	X	50H			
Block Erase Setup/Confirm	2	5	Write	BA	20H	Write	BA	D0H
Full Chip Erase Setup/Confirm	2		Write	X	30H	Write	Χ	D0H
Word/Byte Write Setup/Write	2	5,6	Write	WA	40H	Write	WA	WD
Alternate Word/Byte Write Setup/Write	2	5,6	Write	WA	10H	Write	WA	WD
Multi Word/Byte Write Setup/Confirm	≥4	9	Write	WA	E8H	Write	WA	N-1
Block Erase and (Multi) Word/byte Write Suspend	1	5	Write	Х	В0Н			
Confirm and Block Erase and (Multi) Word/byte Write Resume	1	5	Write	Х	D0H			
Block Lock-Bit Set Setup/Confirm	2	7	Write	BA	60H	Write	BA	01H
Block Lock-Bit Reset Setup/Confirm	2	8	Write	Х	60H	Write	Х	D0H
STS Configuration Level-Mode for Erase and Write (RY/BY# Mode)	2		Write	Х	В8Н	Write	Х	00H
STS Configuration Pulse-Mode for Erase	2		Write	Х	В8Н	Write	Х	01H
STS Configuration Pulse-Mode for Write	2		Write	Х	B8H	Write	Х	02H
STS Configuration Pulse-Mode for Erase and Write	2		Write	Х	B8H	Write	Х	03H

NOTES:

- 1. BUS operations are defined in Table 3 and Table 3.1.
- 2. X=Any valid address within the device.

IA=Identifier Code Address: see Figure 4.

QA=Query Offset Address.

BA=Address within the block being erased or locked.

WA=Address of memory location to be written.

- 3. SRD=Data read from status register. See Table 14 for a description of the status register bits.
 - WD=Data to be written at location WA. Data is latched on the rising edge of WE# or CE# (whichever goes high first).
 - ID=Data read from identifier codes.
 - QD=Data read from query database.
- 4. Following the Read Identifier Codes command, read operations access manufacturer, device and block status codes. See Section 4.2 for read identifier code data.
- 5. If the block is locked, WP# must be at V_{IH} to enable block erase or (multi) word/byte write operations. Attempts to issue a block erase or (multi) word/byte write to a locked block while RP# is V_{IH} .
- 6. Either 40H or 10H are recognized by the WSM as the byte write setup.
- 7. A block lock-bit can be set while WP# is V_{IH} .
- 8. WP# must be at V_{IH} to clear block lock-bits. The clear block lock-bits operation simultaneously clears all block lock-bits.
- 9. Following the Third Bus Cycle, inputs the write address and write data of 'N' times. Finally, input the confirm command 'D0H'.
- 10. Commands other than those shown above are reserved by SHARP for future device implementations and should not be used.



4.1 Read Array Command

Upon initial device power-up and after exit from deep power-down mode, the device defaults to read array mode. This operation is also initiated by writing the Read Array command. The device remains enabled for reads until another command is written. Once the internal WSM has started a block erase, full chip erase, (multi) word/byte write or block lock-bit configuration, the device will not recognize the Read Array command until the WSM completes its operation unless the WSM is suspended via an Erase Suspend and (Multi) Word/byte Write Suspend command. The Read Array command functions independently of the $V_{\rm PP}$ voltage and RP# must be $V_{\rm IH}$.

4.2 Read Identifier Codes Command

The identifier code operation is initiated by writing the Read Identifier Codes command. Following the command write, read cycles from addresses shown in Figure 4 retrieve the manufacturer, device, block lock configuration and block erase status (see Table 5 for identifier code values). To terminate the operation, write another valid command. Like the Read Array command, the Read Identifier Codes command functions independently of the V_{PP} voltage and RP# must be V_{IH} . Following the Read Identifier Codes command, the following information can be read:

Table 5. Identifier Codes

	ner odacs	
Code	Address	Data
Manufacture Code	00000 00001	В0
Device Code	00002 00003	D0
Block Status Code	X0004 ⁽¹⁾ X0005 ⁽¹⁾	
•Block is Unlocked		DQ ₀ =0
•Block is Locked		$DQ_0=1$
 Last erase operation completed successfully 		DQ ₁ =0
 Last erase operation did not completed successfully 		DQ ₁ =1
•Reserved for Future Use		DQ ₂₋₇

NOTE:

 X selects the specific block status code to be read. See Figure 4 for the device identifier code memory map.

4.3 Read Status Register Command

The status register may be read to determine when a block erase, full chip erase, (multi) word/byte write or block lock-bit configuration is complete and whether the operation completed successfully(see Table 14). It may be read at any time by writing the Read Status Register command. After writing this command, all subsequent read operations output data from the status register until another valid command is written. The status register contents are latched on the falling edge of OE# or CE#(Either CE $_0$ # or CE $_1$ #), whichever occurs. OE# or CE#(Either CE $_0$ # or CE $_1$ #) must toggle to V $_{\rm IH}$ before further reads to update the status register latch. The Read Status Register command functions independently of the V $_{\rm PP}$ voltage. RP# must be V $_{\rm IH}$.

The extended status register may be read to determine multi word/byte write availability(see Table 14.1). The extended status register may be read at any time by writing the Multi Word/Byte Write command. After writing this command, all subsequent read operations output data from the extended status register, until another valid command is written. Multi Word/Byte Write command must be re-issued to update the extended status register latch.

4.4 Clear Status Register Command

Status register bits SR.5, SR.4, SR.3 and SR.1 are set to "1"s by the WSM and can only be reset by the Clear Status Register command. These bits indicate various failure conditions (see Table 14). By allowing system software to reset these bits, several operations (such as cumulatively erasing or locking multiple blocks or writing several bytes in sequence) may be performed. The status register may be polled to determine if an error occurs during the sequence.

To clear the status register, the Clear Status Register command (50H) is written. It functions independently of the applied V_{PP} Voltage. RP# must be V_{IH} . This command is not functional during block erase, full chip erase, (multi) word/byte write block lock-bit configuration, block erase suspend or (multi) word/byte write suspend modes.



4.5 Query Command

Query database can be read by writing Query command (98H). Following the command write, read cycle from address shown in Table 7~11 retrieve the critical information to write, erase and otherwise control the flash component. A_0 of query offset address is ignored when X8 mode (BYTE#= V_{II}).

Query data are always presented on the low-byte data output (DQ_0 - DQ_7). In x16 mode, high-byte (DQ_8 - DQ_{15}) outputs 00H. The bytes not assigned to any information or reserved for future use are set to "0". This command functions independently of the V_{PP} voltage. RP# must be V_{IH} .

rable 6. Example of Query Structure Output								
Mode	Offset Address	Output						
		DQ _{15~8}	DQ _{7~0}					
X8 mode	A ₅ , A ₄ , A ₃ , A ₂ , A ₁ , A ₀ 1, 0, 0, 0, 0, 0, 0 (20H) 1, 0, 0, 0, 0, 1 (21H) 1, 0, 0, 0, 1, 1 (22H) 1, 0, 0, 0, 1, 1 (23H)	High Z High Z	"Q" "R" "R"					
X16 mode	A ₅ , A ₄ , A ₃ , A ₂ , A ₁ 1, 0, 0, 0, 0 (10H) 1, 0, 0, 0, 1 (11H)	00H 00H	"Q" "R"					

Table 6 Example of Query Structure Quinut

4.5.1 Block Status Register

This field provides lock configuration and erase status for the specified block. These informations are only available when device is ready (SR.7=1). If block erase or full chip erase operation is finished irregulary, block erase status bit will be set to "1". If bit 1 is "1", this block is invalid.

LHF16KTV

Table 7. Query Block Status Register

Offset (Word Address)	Length	Description
(BA+2)H	01H	Block Status Register bit0 Block Lock Configuration 0=Block is unlocked 1=Block is Locked bit1 Block Erase Status 0=Last erase operation completed successfully 1=Last erase operation not completed successfully bit2-7 reserved for future use

Note:

1. BA=The beginning of a Block Address.



4.5.2 CFI Query Identification String

The Identification String provides verification that the component supports the Common Flash Interface specification. Additionally, it indicates which version of the spec and which Vendor-specified command set(s) is(are) supported.

Table 8. CFI Query Identification String

Offset (Word Address)	Length	Description			
10H,11H,12H	03H	Query Unique ASCII string "QRY" 51H,52H,59H			
13H,14H	02H	imary Vendor Command Set and Control Interface ID Code H,00H (SCS ID Code)			
15H,16H	02H	Address for Primary Algorithm Extended Query Table 31H,00H (SCS Extended Query Table Offset)			
17H,18H	02H	Alternate Vendor Command Set and Control Interface ID Code 0000H (0000H means that no alternate exists)			
19H,1AH	02H	Address for Alternate Algorithm Extended Query Table 0000H (0000H means that no alternate exists)			

4.5.3 System Interface Information

The following device information can be useful in optimizing system interface software.

Table 9. System Information String

Offset (Word Address)	Length	Description	
1BH	01H	V _{CC} Logic Supply Minimum Write/Erase voltage 27H (2.7V)	
1CH	01H	V _{CC} Logic Supply Maximum Write/Erase voltage 55H (5.5V)	
1DH	01H	V _{PP} Programming Supply Minimum Write/Erase voltage 27H (2.7V)	
1EH	01H	V _{PP} Programming Supply Maximum Write/Erase voltage 55H (5.5V)	
1FH	01H	Typical Timeout per Single Byte/Word Write 03H (2 ³ =8µs)	
20H	01H	Typical Timeout for Maximum Size Buffer Write (32 Bytes) 06H (2 ⁶ =64µs)	
21H	01H	Typical Timeout per Individual Block Erase 0AH (0AH=10, 2 ¹⁰ =1024ms)	
22H	01H	Typical Timeout for Full Chip Erase 0FH (0FH=15, 2 ¹⁵ =32768ms)	
23H	01H	Maximum Timeout per Single Byte/Word Write, 2 ^N times of typical. 04H (2 ⁴ =16, 8µsx16=128µs)	
24H	01H	Maximum Timeout Maximum Size Buffer Write, 2 ^N times of typical. 04H (2 ⁴ =16, 64µsx16=1024µs)	
25H	01H	Maximum Timeout per Individual Block Erase, 2 ^N times of typical. 04H (2 ⁴ =16, 1024msx16=16384ms)	
26H	01H	Maximum Timeout for Full Chip Erase, 2 ^N times of typical. 04H (2 ⁴ =16, 32768msx16=524288ms)	



4.5.4 Device Geometry Definition

This field provides critical details of the flash device geometry.

Table 10. Device Geometry Definition

Offset (Word Address)	Length	Description	
27H	01H	Device Size	
		15H (15H=21, 2 ²¹ =2097152=2M Bytes)	
28H,29H	02H	Flash Device Interface description	
		02H,00H (x8/x16 supports x8 and x16 via BYTE#)	
2AH,2BH	02H	Maximum Number of Bytes in Multi word/byte write	
		05H,00H (2 ⁵ =32 Bytes)	
2CH	01H	Number of Erase Block Regions within device	
		01H (symmetrically blocked)	
2DH,2EH	02H	The Number of Erase Blocks	
		1FH,00H (1FH=31 ==> 31+1=32 Blocks)	
2FH,30H	02H	The Number of "256 Bytes" cluster in a Erase block	
		00H,01H (0100H=256 ==>256 Bytes x 256= 64K Bytes in a Erase Block)	

4.5.5 SCS OEM Specific Extended Query Table

Certain flash features and commands may be optional in a vendor-specific algorithm specification. The optional vendor-specific Query table(s) may be used to specify this and other types of information. These structures are defined solely by the flash vendor(s).

Table 11. SCS OEM Specific Extended Query Table

Offset (Word Address)	Length	Description		
31H,32H,33H	03H	PRI		
		50H,52H,49H		
34H	01H	31H (1) Major Version Number , ASCII		
35H	01H	30H (0) Minor Version Number, ASCII		
36H,37H,	04H	0FH,00H,00H,00H		
38H,39H		Optional Command Support		
		bit0=1 : Chip Erase Supported		
		bit1=1 : Suspend Erase Supported		
		bit2=1 : Suspend Write Supported		
		bit3=1 : Lock/Unlock Supported		
		bit4=0 : Queued Erase Not Supported		
		bit5-31=0 : reserved for future use		
3AH	01H	01H		
		Supported Functions after Suspend		
		bit0=1: Write Supported after Erase Suspend		
		bit1-7=0 : reserved for future use		
3BH,3CH	02H	03H,00H		
		Block Status Register Mask		
		bit0=1 : Block Status Register Lock Bit [BSR.0] active		
		bit1=1: Block Status Register Valid Bit [BSR.1] active		
		bit2-15=0 : reserved for future use		
3DH	01H	V _{CC} Logic Supply Optimum Write/Erase voltage(highest performance) 50H(5.0V)		
3EH	01H	V _{PP} Programming Supply Optimum Write/Erase voltage(highest performance) 50H(5.0V)		
3FH	reserved	Reserved for future versions of the SCS Specification		



4.6 Block Erase Command

Block erase is executed one block at a time and initiated by a two-cycle command. A block erase setup is first written, followed by an block erase This confirm. command sequence appropriate sequencing and an address within the block to be erased (erase changes all block data to FFH). Block preconditioning, erase and verify are handled internally by the WSM (invisible to the system). After the two-cycle block erase sequence is written, the device automatically outputs status register data when read (see Figure 5). The CPU can detect block erase completion by analyzing the output data of the STS pin or status register bit SR.7.

When the block erase is complete, status register bit SR.5 should be checked. If a block erase error is detected, the status register should be cleared before system software attempts corrective actions. The CUI remains in read status register mode until a new command is issued.

This two-step command sequence of set-up followed by execution ensures that block contents are not accidentally erased. An invalid Block Erase command sequence will result in both status register bits SR.4 and SR.5 being set to "1". Also, reliable block erasure can only occur when $V_{CC}=V_{CC1/2}$ and $V_{PP}=V_{PPH1/2/3}$. In the absence of this high voltage, block contents are protected against erasure. If block erase is attempted while $V_{PP} \le V_{PPLK}$, SR.3 and SR.5 will be set to "1". Successful block erase requires that the corresponding block lock-bit be cleared or if set, that WP#= V_{IH} . If block erase is attempted when the corresponding block lock-bit is set and WP#= V_{IL} , SR.1 and SR.5 will be set to "1".

4.7 Full Chip Erase Command

This command followed by a confirm command (D0H) erases all of the unlocked blocks. A full chip

erase setup is first written, followed by a full chip erase confirm. After a confirm command is written, device erases the all unlocked blocks from block 0 to Block 31 block by block. This command sequence requires appropriate sequencing. Block preconditioning, erase and verify are handled internally by the WSM (invisible to the system). After the two-cycle full chip erase sequence is written, the device automatically outputs status register data when read (see Figure 6). The CPU can detect full chip erase completion by analyzing the output data of the STS pin or status register bit SR.7.

When the full chip erase is complete, status register bit SR.5 should be checked. If erase error is detected, the status register should be cleared before system software attempts corrective actions. The CUI remains in read status register mode until a new command is issued. If error is detected on a block during full chip erase operation, WSM stops erasing. Reading the block valid status by issuing Read ID Codes command or Query command informs which blocks failed to its erase.

This two-step command sequence of set-up followed by execution ensures that block contents are not accidentally erased. An invalid Full Chip Erase command sequence will result in both status register bits SR.4 and SR.5 being set to "1". Also, reliable full chip erasure can only occur when $V_{CC}=V_{CC1/2}$ and $V_{PP}=V_{PPH1/2/3}$. In the absence of this high voltage, block contents are protected against erasure. If full chip erase is attempted while $V_{PP}\leq V_{PPLK}$, SR.3 and SR.5 will be set to "1". When WP#= V_{IH} , all blocks are erased independent of block lock-bits status. When WP#= V_{IL} , only unlocked blocks are erased. In this case, SR.1 and SR.5 will not be set to "1". Full chip erase can not be suspended.



4.8 Word/Byte Write Command

Word/byte write is executed by a two-cycle command sequence. Word/Byte Write setup (standard 40H or alternate 10H) is written, followed by a second write that specifies the address and data (latched on the rising edge of WE#). The WSM then takes over, controlling the word/byte write and write verify algorithms internally. After the word/byte write sequence is written, the device automatically outputs status register data when read (see Figure 7). The CPU can detect the completion of the word/byte write event by analyzing the STS pin or status register bit SR.7.

When word/byte write is complete, status register bit SR.4 should be checked. If word/byte write error is detected, the status register should be cleared. The internal WSM verify only detects errors for "1"s that do not successfully write to "0"s. The CUI remains in read status register mode until it receives another command.

Reliable word/byte writes can only occur when $V_{CC}=V_{CC1/2}$ and $V_{PP}=V_{PPH1/2/3}$. In the absence of this high voltage, memory contents are protected against word/byte writes. If word/byte write is attempted while $V_{PP} \le V_{PPLK}$, status register bits SR.3 and SR.4 will be set to "1". Successful word/byte write requires that the corresponding block lock-bit be cleared or, if set, that WP#= V_{IH} . If word/byte write is attempted when the corresponding block lock-bit is set and WP#= V_{IL} , SR.1 and SR.4 will be set to "1". Word/byte write operations with $V_{IL} < WP\# < V_{IH}$ produce spurious results and should not be attempted.

4.9 Multi Word/Byte Write Command

Multi word/byte write is executed by at least four-cycle or up to 35-cycle command sequence. Up to 32 bytes in x8 mode (16 words in x16 mode) can be loaded into the buffer and written to the Flash Array. First, multi word/byte write setup (E8H) is written with the write address. At this point, the device automatically outputs extended status register data (XSR) when read (see Figure 8, 9). If extended status register bit XSR.7 is 0, no Multi Word/Byte Write command is available and multi word/byte write setup which just has been written is ignored. To retry,

continue monitoring XSR.7 by writing multi word/byte write setup with write address until XSR.7 transitions to 1. When XSR.7 transitions to 1, the device is ready for loading the data to the buffer. A word/byte count (N)-1 is written with write address. After writing a word/byte count(N)-1, the device automatically turns back to output status register data. The word/byte count (N)-1 must be less than or equal to 1FH in x8 mode (0FH in x16 mode). On the next write, device start address is written with buffer data. Subsequent writes provide additional device address and data, depending on the count. All subsequent address must lie within the start address plus the count. After the final buffer data is written, write confirm (D0H) must be written. This initiates WSM to begin copying the buffer data to the Flash Array. An invalid Multi Word/Byte Write command sequence will result in both status register bits SR.4 and SR.5 being set to "1". For additional multi word/byte write, write another multi word/byte write setup and check XSR.7. The Multi Word/Byte Write command can be gueued while WSM is busy as long as XSR.7 indicates "1", because LH28F160S3HNS-TV has two buffers. If an error occurs while writing, the device will stop writing and flush next multi word/byte write command loaded in multi word/byte write command. Status register bit SR.4 will be set to "1". No multi word/byte write command is available if either SR.4 or SR.5 are set to "1". SR.4 and SR.5 should be cleared before issuing multi word/byte write command. If a multi word/byte write command is attempted past an erase block boundary, the device will write the data to Flash Array up to an erase block boundary and then stop writing. Status register bits SR.4 and SR.5 will be set to "1".

Reliable multi byte writes can only occur when $V_{CC}=V_{CC1/2}$ and $V_{PP}=V_{PPH1/2/3}$. In the absence of this high voltage, memory contents are protected against multi word/byte writes. If multi word/byte write is attempted while $V_{PP} \le V_{PPLK}$, status register bits SR.3 and SR.4 will be set to "1". Successful multi word/byte write requires that the corresponding block lock-bit be cleared or, if set, that WP#= V_{IH} . If multi byte write is attempted when the corresponding block lock-bit is set and WP#= V_{IL} , SR.1 and SR.4 will be set to "1".



4.10 Block Erase Suspend Command

The Block Erase Suspend command allows blockerase interruption to read or (multi) word/byte-write data in another block of memory. Once the blockerase process starts, writing the Block Erase Suspend command requests that the WSM suspend the block erase sequence at a predetermined point in the algorithm. The device outputs status register data when read after the Block Erase Suspend command is written. Polling status register bits SR.7 and SR.6 can determine when the block erase operation has been suspended (both will be set to "1"). STS will also transition to High Z. Specification t_{WHRH2} defines the block erase suspend latency.

At this point, a Read Array command can be written to read data from blocks other than that which is suspended. A (Multi) Word/Byte Write command sequence can also be issued during erase suspend to program data in other blocks. Using the (Multi) Word/Byte Write Suspend command (see Section 4.11), a (multi) word/byte write operation can also be suspended. During a (multi) word/byte write operation with block erase suspended, status register bit SR.7 will return to "0" and the STS (if set to RY/BY#) output will transition to V_{OL}. However, SR.6 will remain "1" to indicate block erase suspend status.

The only other valid commands while block erase is suspended are Read Status Register and Block Erase Resume. After a Block Erase Resume command is written to the flash memory, the WSM will continue the block erase process. Status register bits SR.6 and SR.7 will automatically clear and STS will return to $V_{\rm OL}$. After the Erase Resume command is written, the device automatically outputs status register data when read (see Figure 10). $V_{\rm PP}$ must remain at $V_{\rm PPH1/2/3}$ (the same $V_{\rm PP}$ level used for block erase) while block erase is suspended. RP# must also remain at $V_{\rm IH}$. WP# must also remain at the same level used for block erase. BYTE# must be the same level as writing the Block Erase command when the Block Erase Resume command is written. Block erase cannot resume until (multi) word/byte

write operations initiated during block erase suspend have completed.

4.11 (Multi) Word/Byte Write Suspend Command

The (Multi) Word/Byte Write Suspend command allows (multi) word/byte write interruption to read data in other flash memory locations. Once the (multi) word/byte write process starts, writing the (Multi) Word/Byte Write Suspend command requests that the WSM suspend the (multi) word/byte write sequence at a predetermined point in the algorithm. The device continues to output status register data when read after the (Multi) Word/Byte Write Suspend command is written. Polling status register bits SR.7 and SR.2 can determine when the (multi) word/byte write operation has been suspended (both will be set to "1"). STS will also transition to High Z. Specification t_{WHRH1} defines the (multi) word/byte write suspend latency.

At this point, a Read Array command can be written to read data from locations other than that which is suspended. The only other valid commands while (multi) word/byte write is suspended are Read Status Register and (Multi) Word/Byte Write Resume. After (Multi) Word/Byte Write Resume command is written to the flash memory, the WSM will continue the (multi) word/byte write process. Status register bits SR.2 and SR.7 will automatically clear and STS will return to VOI. After the (Multi) Word/Byte Write command is written, the device automatically outputs status register data when read (see Figure 11). VPP must remain at $V_{PPH1/2/3}$ (the same V_{PP} level used for (multi) word/byte write) while in (multi) word/byte write suspend mode. RP# must also remain at VIH. WP# must also remain at the same level used for (multi) word/byte write. BYTE# must be the same level as writing the (Multi) Word/Byte Write command when the (Multi) Word/Byte Write Resume command is written.



4.12 Set Block Lock-Bit Command

A flexible block locking and unlocking scheme is enabled via block lock-bits. The block lock-bits gate program and erase operations With WP#= V_{IH} , individual block lock-bits can be set using the Set Block Lock-Bit command. See Table 13 for a summary of hardware and software write protection options.

Set block lock-bit is executed by a two-cycle command sequence. The set block lock-bit setup along with appropriate block or device address is written followed by either the set block lock-bit confirm (and an address within the block to be locked). The WSM then controls the set block lock-bit algorithm. After the sequence is written, the device automatically outputs status register data when read (see Figure 12). The CPU can detect the completion of the set block lock-bit event by analyzing the STS pin output or status register bit SR.7.

When the set block lock-bit operation is complete, status register bit SR.4 should be checked. If an error is detected, the status register should be cleared. The CUI will remain in read status register mode until a new command is issued.

This two-step sequence of set-up followed by execution ensures that block lock-bits are not accidentally set. An invalid Set Block Lock-Bit command will result in status register bits SR.4 and SR.5 being set to "1". Also, reliable operations occur only when $V_{\rm CC}=V_{\rm CC1/2}$ and $V_{\rm PP}=V_{\rm PPH1/2/3}$. In the absence of this high voltage, block lock-bit contents are protected against alteration.

A successful set block lock-bit operation requires WP#= V_{IH} . If it is attempted with WP#= V_{IL} , SR.1 and SR.4 will be set to "1" and the operation will fail. Set block lock-bit operations with WP#< V_{IH} produce spurious results and should not be attempted.

4.13 Clear Block Lock-Bits Command

All set block lock-bits are cleared in parallel via the Clear Block Lock-Bits command. With WP#=VIH,

block lock-bits can be cleared using only the Clear Block Lock-Bits command. See Table 13 for a summary of hardware and software write protection options.

Clear block lock-bits operation is executed by a twocycle command sequence. A clear block lock-bits setup is first written. After the command is written, the device automatically outputs status register data when read (see Figure 13). The CPU can detect completion of the clear block lock-bits event by analyzing the STS Pin output or status register bit SR.7.

When the operation is complete, status register bit SR.5 should be checked. If a clear block lock-bit error is detected, the status register should be cleared. The CUI will remain in read status register mode until another command is issued.

This two-step sequence of set-up followed by execution ensures that block lock-bits are not accidentally cleared. An invalid Clear Block Lock-Bits command sequence will result in status register bits SR.4 and SR.5 being set to "1". Also, a reliable clear block lock-bits operation can only occur when $V_{CC}=V_{CC1/2}$ and $V_{PP}=V_{PPH1/2/3}$. If a clear block lockbits operation is attempted while V_{PP}≤V_{PPI K}, SR.3 and SR.5 will be set to "1". In the absence of this high voltage, the block lock-bits content are protected against alteration. A successful clear block lock-bits operation requires WP#=VIH. If it is attempted with WP#=V_{II}, SR.1 and SR.5 will be set to "1" and the operation will fail. Clear block lock-bits operations with V_{IH}<RP# produce spurious results and should not be attempted.

If a clear block lock-bits operation is aborted due to V_{PP} or V_{CC} transitioning out of valid range or RP# active transition, block lock-bit values are left in an undetermined state. A repeat of clear block lock-bits is required to initialize block lock-bit contents to known values.

19



4.14 STS Configuration Command

The Status (STS) pin can be configured to different states using the STS Configuration command. Once the STS pin has been configured, it remains in that configuration until another configuration command is issued, the device is powered down or RP# is set to V_{IL} . Upon initial device power-up and after exit from deep power-down mode, the STS pin defaults to RY/BY# operation where STS low indicates that the WSM is busy. STS High Z indicates that the WSM is ready for a new operation.

To reconfigure the STS pin to other modes, the STS Configuration is issued followed by the appropriate configuration code. The three alternate configurations are all pulse mode for use as a system interrupt. The STS Configuration command functions independently of the V_{PP} voltage and RP# must be V_{IH} .

Table 12. STS Configuration Coding Description

Configuration Bits	Effects
00H	Set STS pin to default level mode (RY/BY#). RY/BY# in the default level-mode of operation will indicate WSM status condition.
01H	Set STS pin to pulsed output signal for specific erase operation. In this mode, STS provides low pulse at the completion of BLock Erase, Full Chip Erase and Clear Block Lock-bits operations.
02H	Set STS pin to pulsed output signal for a specific write operation. In this mode, STS provides low pulse at the completion of (Multi) Byte Write and Set Block Lock-bit operation.
03H	Set STS pin to pulsed output signal for specific write and erase operation. STS provides low pulse at the completion of Block Erase, Full Chip Erase, (Multi) Word/Byte Write and Block Lock-bit Configuration operations.

Table 13. Write Protection Alternatives

Table 101 Tillion 1 Cooling 1 Allonia 1 Too					
Operation	Block Lock-Bit	WP#	Effect		
Block Erase,	0	V _{IL} or V _{IH}	Block Erase and (Multi) Word/Byte Write Enabled		
(Multi) Word/Byte	1	V _{IL}	Block is Locked. Block Erase and (Multi) Word/Byte Write		
Write	' '	│ VIL	Disabled		
		\/	Block Lock-Bit Override. Block Erase and (Multi) Word/Byte		
		V_{IH}	Write Enabled		
Full Chip Erase	0,1	V _{II}	All unlocked blocks are erased, locked blocks are not erased		
	X	V _{IH}	All blocks are erased		
Set Block Lock-Bit	X	V _{II}	Set Block Lock-Bit Disabled		
		V _{IH}	Set Block Lock-Bit Enabled		
Clear Block Lock-Bits	X	V _{IL}	Clear Block Lock-Bits Disabled		
		V _{IH}	Clear Block Lock-Bits Enabled		



		Tabl	e 14. Status	Register Defin	ition		
WSMS	BESS	ECBLBS	WSBLBS	VPPS	WSS	DPS	R
7	6	5	4	3	2	1	0
1 = Ready 0 = Busy SR.6 = BLOC 1 = Block 0 = Block SR.5 = ERAS STAT 1 = Error 0 = Succe SR.4 = WRIT 1 = Error 0 = Succe SR.3 = V _{PP} S 1 = V _{PP} L 0 = V _{PP} C SR.2 = WRIT 1 = Write 0 = Write SR.1 = DEVIC 1 = Block	EK ERASE SUS Erase Suspenderase in Progresse in Progresse in Progress in Erase or Clessful Erase or E AND SET BLE in Write or Set in Erase in Write or Set in	SPEND STATU ded ress/Completed R BLOCK LOCK ear Block Lock-I Clear Block Lock LOCK LOCK-B Block Lock-Bit Set Block Lock eration Abort STATUS ompleted STATUS	JS d :K-BITS Bits ock-Bits BIT STATUS t c-Bit	erase, (multi) configuration SR.6-0 are in S	word/byte write completion. valid while SR. and SR.4 are "1 nulti) word/byte or STS configuence was en the provide a constant of the provide a constant of the provide a constant of the word of the w	"s after a block of write, block lock ration attempt, tered." attinuous indicates and indicates and indicates anteed to report anteed to report terrogates block ase, full chip erace, full chip erace, full chip erace, terrogates block ase, full chip erace, terrogates block ase, full chip erace, terrogates block ase, full chip erace, terrogates block configurations attemption at the block lock configuration at the block lock lock lock lock lock lock lock	erase, full ck-bit an improper to V _{PP} level word/byte and on of block k lock-bit, ase, (multi) on commanding on the set and/or figuration is command


SR.0 = RESERVED FOR FUTURE ENHANCEMENTS

Table 14.1. Extended Status Register Definition

out when polling the status register.

П	Table I III = Attended Status (toglets, Delinition							
	SMS	R	R	R	R	R	R	R
	7	6	5	4	3	2	1	0

XSR.7 = STATE MACHINE STATUS 1 = Multi Word/Byte Write available 0 = Multi Word/Byte Write not available XSR.6-0=RESERVED FOR FUTURE ENHANCEMENTS XSR.6-0 is reserved for future use and should be masked out when polling the extended status register.




Bus Operation	Command	Comments
Write	Read Status Register	Data=70H Addr=X
Read		Status Register Data
Standby		Check SR.7 1=WSM Ready 0=WSM Busy
Write	Erase Setup	Data=20H Addr=Within Block to be Erased
Write	Erase Confirm	Data=D0H Addr=Within Block to be Erased
Read		Status Register Data
Standby		Check SR.7 1=WSM Ready 0=WSM Busy

Repeat for subsequent block erasures.

Full status check can be done after each block erase or after a sequence of block erasures.

Write FFH after the last operation to place device in read array mode.

FULL STATUS CHECK PROCEDURE




Bus Operation	Command	Comments
Standby		Check SR.3 1=V _{PP} Error Detect
Standby		Check SR.1 1=Device Protect Detect WP#=V _{IL} ,Block Lock-Bit is Set Only required for systems implementing lock-bit configuration
Standby		Check SR.4,5 Both 1=Command Sequence Error
Standby		Check SR.5 1=Block Erase Error

SR.5,SR.4,SR.3 and SR.1 are only cleared by the Clear Status Register Command in cases where multiple blocks are erased before full status is checked.

If error is detected, clear the Status Register before attempting retry or other error recovery.

Figure 5. Automated Block Erase Flowchart

21




Bus Operation	Command	Comments
Write	Read Status Register	Data=70H Addr=X
Read		Status Register Data
Standby		Check SR.7 1=WSM Ready 0=WSM Busy
Write	Full Chip Erase Setup	Data=30H Addr=X
Write	Full Chip Erase Confirm	Data=D0H Addr=X
Read		Status Register Data
Standby		Check SR.7 1=WSM Ready 0=WSM Busy

Full status check can be done after each full chip erase.

Write FFH after the last operation to place device in read array mode.

FULL STATUS CHECK PROCEDURE




Bus Operation	Command	Comments			
Standby		Check SR.3 1=V _{PP} Error Detect			
Standby		Check SR.4,5 Both 1=Command Sequence Error			
Standby		Check SR.5 1=Full Chip Erase Error			

SR.5,SR.4,SR.3 and SR.1 are only cleared by the Clear Status Register Command in cases where multiple blocks are erased before full status is checked.

If error is detected, clear the Status Register before attempting retry or other error recovery.

Figure 6. Automated Full Chip Erase Flowchart

23




Bus Operation	Command	Comments			
Write	Read Status Register	Data=70H Addr=X			
Read		Status Register Data			
Standby		Check SR.7 1=WSM Ready 0=WSM Busy			
Write	Setup Word/Byte Write	Data=40H or 10H Addr=Location to Be Written			
Write	Word/Byte Write	Data=Data to Be Written Addr=Location to Be Written			
Read		Status Register Data			
Standby		Check SR.7 1=WSM Ready 0=WSM Busy			

Repeat for subsequent word/byte writes.

SR full status check can be done after each word/byte write, or after a sequence of word/byte writes.

Write FFH after the last word/byte write operation to place device in read array mode.

FULL STATUS CHECK PROCEDURE




Command	Comments		
	Check SR.3 1=V _{PP} Error Detect		
	Check SR.1 1=Device Protect Detect WP#=V _{IL} .Block Lock-Bit is Set Only required for systems implementing lock-bit configuration		
	Check SR.4 1=Data Write Error		
	Command		

SR.4,SR.3 and SR.1 are only cleared by the Clear Status Register command in cases where multiple locations are written before full status is checked.

If error is detected, clear the Status Register before attempting retry or other error recovery.

Figure 7. Automated Word/byte Write Flowchart



Bus Operation	Command	Comments
Write	Setup Multi Word/Byte Write	Data=E8H Addr=Start Address
Read		Extended Status Register Data
Standby		Check XSR.7 1=Multi Word/Byte Write Ready 0=Multi Word/Byte Write Busy
Write (Note1)		Data=Word or Byte Count (N)-1 Addr=Start Address
Write (Note2,3)		Data=Buffer Data Addr=Start Address
Write (Note4,5)		Data=Buffer Data Addr=Device Address
Write		Data=D0H Addr=X
Read		Status Register Data
Standby		Check SR.7 1=WSM Ready 0=WSM Busy

- 1. Byte or word count values on DQ_{0-7} are loaded into the count register.
- 2. Write Buffer contents will be programmed at the start address.
- Align the start address on a Write Buffer boundary for maximum programming performance.
- 4.The device aborts the Multi Word/Byte Write command if the current address is outside of the original block address.
- 5.The Status Register indicates an "improper command sequence" if the Multi Word/Byte command is aborted. Follow this with a Clear Status Register command. SR full status check can be done after each multi word/byte write, or after a sequence of multi word/byte writes.
- Write FFH after the last multi word/byte write operation to place device in read array mode.

Figure 8. Automated Multi Word/Byte Write Flowchart




Figure 9. Full Status Check Procedure for Automated Multi Word/Byte Write




Figure 10. Block Erase Suspend/Resume Flowchart





Figure 11. (Multi) Word/Byte Write Suspend/Resume Flowchart




Bus Operation	Command	Comments
Write	Set Block Lock-Bit Setup	Data=60H Addr=Block Address
Write	Set Block Lock-Bit Confirm	Data=01H, Addr=Block Address
Read		Status Register Data
Standby		Check SR.7 1=WSM Ready 0=WSM Busy

Repeat for subsequent block lock-bit set operations.

Full status check can be done after each block lock-bit set operation or after a sequence of block lock-bit set operations.

Write FFH after the last block lock-bit set operation to place device in read array mode.

FULL STATUS CHECK PROCEDURE




Bus Operation	Command	Comments
Standby		Check SR.3 1=V _{PP} Error Detect
Standby		Check SR.1 1=Device Protect Detect WP#=V _{IL}
Standby		Check SR.4,5 Both 1=Command Sequence Error
Standby		Check SR.4 1=Set Block Lock-Bit Error

SR.5,SR.4,SR.3 and SR.1 are only cleared by the Clear Status Register command in cases where multiple block lock-bits are set before full status is checked.

If error is detected, clear the Status Register before attempting retry or other error recovery.

Figure 12. Set Block Lock-Bit Flowchart


29



Bus Operation	Command	Comments		
Write	Clear Block Lock-Bits Setup	Data=60H Addr=X		
Write	Clear Block Lock-Bits Confirm	Data=D0H Addr=X		
Read		Status Register Data		
Standby		Check SR.7 1=WSM Ready 0=WSM Busy		
Write FFH after the Clear Block Lock-Bits operation to				

place device in read array mode.

FULL STATUS CHECK PROCEDURE



Bus Operation	Command	Comments
Standby		Check SR.3 1=V _{PP} Error Detect
Standby		Check SR.1 1=Device Protect Detect WP#=V _{IL}
Standby		Check SR.4,5 Both 1=Command Sequence Error
Standby		Check SR.5 1=Clear Block Lock-Bits Error

If error is detected, clear the Status Register before attempting

retry or other error recovery.

Figure 13. Clear Block Lock-Bits Flowchart



5 DESIGN CONSIDERATIONS

5.1 Three-Line Output Control

The device will often be used in large memory arrays. SHARP provides three control inputs to accommodate multiple memory connections. Three-Line control provides for:

- a. Lowest possible memory power dissipation.
- b. Complete assurance that data bus contention will not occur.

To use these control inputs efficiently, an address decoder should enable CE# while OE# should be connected to all memory devices and the system's READ# control line. This assures that only selected memory devices have active outputs while deselected memory devices are in standby mode. RP# should be connected to the system POWERGOOD signal to prevent unintended writes during system power transitions. POWERGOOD should also toggle during system reset.

5.2 STS and Block Erase, Full Chip Erase, (Multi) Word/Byte Write and Block Lock-Bit Configuration Polling

STS is an open drain output that should be connected to V_{CC} by a pullup resistor to provide a hardware method of detecting block erase, full chip erase, (multi) word/byte write and block lock-bit configuration completion. In default mode, it transitions low after block erase, full chip erase, (multi) word/byte write or block lock-bit configuration commands and returns to V_{OH} when the WSM has finished executing the internal algorithm. For alternate STS pin configurations, see the Configuration command.

STS can be connected to an interrupt input of the system CPU or controller. It is active at all times.

STS, in default mode, is also High Z when the device is in block erase suspend (with (multi) word/byte write inactive), (multi) word/byte write suspend or deep power-down modes.

5.3 Power Supply Decoupling

Flash memory power switching characteristics require careful device decoupling. System designers are interested in three supply current issues; standby current levels, active current levels and transient peaks produced by falling and rising edges of CE# and OE#. Transient current magnitudes depend on the device outputs' capacitive and inductive loading. Two-line control and proper decoupling capacitor selection will suppress transient voltage peaks. Each device should have a 0.1µF ceramic capacitor connected between its V_{CC} and GND and between its V_{PP} and GND. These high-frequency, low inductance capacitors should be placed as close as possible to package leads. Additionally, for every eight devices, a 4.7µF electrolytic capacitor should be placed at the array's power supply connection between V_{CC} and GND. The bulk capacitor will overcome voltage slumps caused by PC board trace inductance.

5.4 V_{PP} Trace on Printed Circuit Boards

Updating flash memories that reside in the target system requires that the printed circuit board designer pay attention to the V_{PP} Power supply trace. The V_{PP} pin supplies the memory cell current for block erase, full chip erase, (multi) word/byte write and block lock-bit configuration. Use similar trace widths and layout considerations given to the V_{CC} power bus. Adequate V_{PP} supply traces and decoupling will decrease V_{PP} voltage spikes and overshoots.



5.5 V_{CC}, V_{PP}, RP# Transitions

Block erase, full chip erase, (multi) word/byte write and block lock-bit configuration are not guaranteed if V_{PP} falls outside of a valid $V_{PPH1/2/3}$ range, V_{CC} falls outside of a valid $V_{CC1/2}$ range, or $RP\#=V_{IL}.$ If V_{PP} error is detected, status register bit SR.3 is set to "1" along with SR.4 or SR.5, depending on the attempted operation. If RP# transitions to V_{IL} during block erase, full chip erase, (multi) word/byte write or block lock-bit configuration, STS(if set to RY/BY# mode) will remain low until the reset operation is complete. Then, the operation will abort and the device will enter deep power-down. The aborted operation may leave data partially altered. Therefore, the command sequence must be repeated after normal operation is restored. Device power-off or RP# transitions to V_{IL} clear the status register.

The CUI latches commands issued by system software and is not altered by V_{PP} or CE# transitions or WSM actions. Its state is read array mode upon power-up, after exit from deep power-down or after V_{CC} transitions below V_{LKO} .

After block erase, full chip erase, (multi) word/byte write or block lock-bit configuration, even after V_{PP} transitions down to V_{PPLK} , the CUI must be placed in read array mode via the Read Array command if subsequent access to the memory array is desired.

5.6 Power-Up/Down Protection

The device is designed to offer protection against accidental block and full chip erasure, (multi) word/byte writing or block lock-bit configuration during power transitions. Upon power-up, the device is indifferent as to which power supply (V_{PP} or V_{CC})

powers-up first. Internal circuitry resets the CUI to read array mode at power-up.

A system designer must guard against spurious writes for V_{CC} voltages above V_{LKO} when V_{PP} is active. Since both WE# and CE# must be low for a command write, driving either to V_{IH} will inhibit writes. The CUI's two-step command sequence architecture provides added level of protection against data alteration.

In-system block lock and unlock capability prevents inadvertent data alteration. The device is disabled while RP#= V_{II} regardless of its control inputs state.

5.7 Power Dissipation

When designing portable systems, designers must consider battery power consumption not only during device operation, but also for data retention during system idle time. Flash memory's nonvolatility increases usable battery life because data is retained when system power is removed.

In addition, deep power-down mode ensures extremely low power consumption even when system power is applied. For example, portable computing products and other power sensitive applications that use an array of devices for solid-state storage can consume negligible power by lowering RP# to V_{IL} standby or sleep modes. If access is again needed, the devices can be read following the t_{PHQV} and t_{PHWL} wake-up cycles required after RP# is first raised to V_{IH} . See AC Characteristics— Read Only and Write Operations and Figures 17, 18, 19, 20 for more information.



6 ELECTRICAL SPECIFICATIONS

6.1 Absolute Maximum Ratings*

*WARNING: Stressing the device beyond the "Absolute Maximum Ratings" may cause permanent damage. These are stress ratings only. Operation beyond the "Operating Conditions" is not recommended and extended exposure beyond the "Operating Conditions" may affect device reliability.

NOTES:

- 1. Operating temperature is for extended temperature product defined by this specification.
- 2. All specified voltages are with respect to GND. Minimum DC voltage is -0.5V on input/output pins and -0.2V on V_{CC} and V_{PP} pins. During transitions, this level may undershoot to -2.0V for periods <20ns. Maximum DC voltage on input/output pins and V_{CC} is V_{CC} +0.5V which, during transitions, may overshoot to V_{CC} +2.0V for periods <20ns.
- 3. Output shorted for no more than one second. No more than one output shorted at a time.

6.2 Operating Conditions

Temperature and V_{CC} Operating Conditions

Symbol	Parameter	Min.	Max.	Unit	Test Condition
T _A	Operating Temperature	-40	+85	°C	Ambient Temperature
V _{CC1}	V _{CC} Supply Voltage (2.7V-3.6V)	2.7	3.6	V	
	V _{CC} Supply Voltage (3.3V±0.3V)	3.0	3.6	V	

6.2.1 CAPACITANCE(1)

 $T_A=+25$ °C, f=1MHz

Symbol	Parameter	Тур.	Max.	Unit	Condition
C _{IN}	Input Capacitance	7	10	рF	V _{IN} =0.0V
C _{OUT}	Output Capacitance	9	12	pF	V _{OUT} =0.0V

NOTE:

1. Sampled, not 100% tested.



6.2.2 AC INPUT/OUTPUT TEST CONDITIONS




Figure 14. Transient Input/Output Reference Waveform for V_{CC}=2.7V-3.6V




Figure 15. Transient Input/Output Reference Waveform for V_{CC}=3.3V±0.3V




Figure 16. Transient Equivalent Testing Load Circuit

Test Configuration Capacitance Loading Value
Test Configuration C₁ (pF)

V_{CC}=3.3V±0.3V, 2.7V-3.6V



6.2.3 DC CHARACTERISTICS

DC Characteristics

			V _{CC} =	=2.7V	V _{CC} =	V _{CC} =3.3V		V _{CC} =3.3V		Test	
Sym.	Parameter	Notes	Тур.	Max.	Тур.	Max.	Unit	Conditions			
ILI	Input Load Current	1		±0.5		±0.5	μA	V _{CC} =V _{CC} Max. V _{IN} =V _{CC} or GND			
I _{LO}	Output Leakage Current	1		±0.5		±0.5	μA	V _{CC} =V _{CC} Max. V _{OUT} =V _{CC} or GND			
I _{CCS}	V _{CC} Standby Current	1,3,6	20	100	20	100	μA	CMOS Inputs $V_{CC}=V_{CC}Max$. $CE\#=RP\#=V_{CC}\pm0.2V$			
			1	4	1	4	mA	TTL Inputs V _{CC} =V _{CC} Max. CE#=RP#=V _{IH}			
I _{CCD}	V _{CC} Deep Power-Down Current	1		20		20	μA	RP#=GND±0.2V I _{OUT} (STS)=0mA			
I _{CCR}	V _{CC} Read Current	1,5,6		25		25	mA	CMOS Inputs V _{CC} =V _{CC} Max. CE#=GND			
				30		30	mA				
I _{CCW}	V _{CC} Write Current	1,7		17	_		mA	V _{PP} =2.7V-3.6V			
	((Multi) W/B Write or			17		17	mA	V _{PP} =3.3V±0.3V			
	Set Block Lock Bit)			17		17	mA	V _{PP} =5.0V±0.5V			
I _{CCE}	V _{CC} Erase Current	1,7		17	_	_	mA	V _{PP} =2.7V-3.6V			
	(Block Erase, Full Chip			17		17	mA	V _{PP} =3.3V±0.3V			
	Erase, Clear Block Lock Bits)			17		17	mA	V _{PP} =5.0V±0.5V			
I _{CCES}	V _{CC} Write or Block Erase Suspend Current	1,2	1	6	1	6	mA	CE#=V _{IH}			
I _{PPS}	V _{PP} Standby Current	1	±2	±15	±2	±15	μA	$V_{PP} \leq V_{CC}$			
I_{PPR}	V _{PP} Read Current	1	10	200	10	200	μA	$V_{PP}>V_{CC}$			
I _{PPD}	V _{PP} Deep Power-Down Current	1	0.1	5	0.1	5	μA	RP#=GND±0.2V			
I _{PPW}	V _{PP} Write Current	1,7		80	_	_	mA	V _{PP} =2.7V-3.6V			
	((Multi) W/B Write or			80		80	mA	V _{PP} =3.3V±0.3V			
	Set Block Lock Bit)			80		80	mA	V _{PP} =5.0V±0.5V			
I _{PPE}	V _{PP} Erase Current	1,7		40			mA	V _{PP} =2.7V-3.6V			
	(Block Erase, Full Chip			40		40	mA	V _{PP} =3.3V±0.3V			
	Erase, Clear Block Lock Bits)			40		40	mA	V _{PP} =5.0V±0.5V			
I _{PPWS}	V _{PP} Write or Block Erase Suspend Current	1	10	200	10	200	μA	V _{PP} =V _{PPH1/2/3}			

			V _{CC} =	=2.7V	V V _{CC} =3.3V			Test
Sym.	Parameter	Notes	Min.	Max.	Min.	Max.	Unit	Conditions
V _{IL}	Input Low Voltage	7	-0.5	0.8	-0.5	0.8	V	
V _{IH}	Input High Voltage	7	2.0	V _{CC} +0.5	2.0	V _{CC} +0.5	V	
V _{OL}	Output Low Voltage	3,7		0.4		0.4	V	V _{CC} =V _{CC} Min. I _{OL} =2mA
V _{OH1}	Output High Voltage (TTL)	3,7	2.4		2.4		V	V _{CC} =V _{CC} Min. I _{OH} =-2.5mA
V _{OH2}	Output High Voltage (CMOS)	3,7	0.85 V _{CC}		0.85 V _{CC}		V	V _{CC} =V _{CC} Min. I _{OH} =-2.5mA
			V _{CC} -0.4		V _{CC} -0.4		V	V _{CC} =V _{CC} Min. I _{OH} =-100μA
V _{PPLK}	V _{PP} Lockout Voltage during Normal Operations	4,7		1.5		1.5	V	
V _{PPH1}	V _{PP} Voltage during Write or Erase Operations		2.7	3.6			V	
V _{PPH2}	V _{PP} Voltage during Write or Erase Operations		3.0	3.6	3.0	3.6	V	
V _{PPH3}	V _{PP} Voltage during Write or Erase Operations		4.5	5.5	4.5	5.5	V	
V_{LKO}	V _{CC} Lockout Voltage		2.0		2.0		V	

- All currents are in RMS unless otherwise noted. Typical values at nominal V_{CC} voltage and T_A=+25°C.
- 2. I_{CCWS} and I_{CCES} are specified with the device de-selected. If read or byte written while in erase suspend mode, the device's current draw is the sum of I_{CCWS} or I_{CCES} and I_{CCR} or I_{CCW} , respectively.
- 4. Block erases, full chip erases, (multi) word/byte writes and block lock-bit configurations are inhibited when $V_{PP} \le V_{PPLK}$, and not guaranteed in the range between V_{PPLK} (max.) and V_{PPH1} (min.), between V_{PPH1} (max.) and V_{PPH2}(min.), between V_{PPH2}(max.) and V_{PPH3}(min.) and above V_{PPH3}(max.).

 5. Automatic Power Savings (APS) reduces typical I_{CCR} to 3mA at 2.7V and 3.3V V_{CC} in static operation.
- CMOS inputs are either V_{CC}±0.2V or GND±0.2V. TTL inputs are either V_{IL} or V_{IH}.
 Sampled, not 100% tested.



6.2.4 AC CHARACTERISTICS - READ-ONLY OPERATIONS(1)

 V_{CC} =2.7V-3.6V, T_{A} =-40°C to +85°C

	Versions ⁽⁴⁾		LH28F160)S3H-L120	
Sym.	Parameter	Notes	Min.	Max.	Unit
t _{AVAV}	Read Cycle Time		120		ns
t _{AVQV}	Address to Output Delay			120	ns
t _{ELQV}	CE# to Output Delay	2		120	ns
t _{PHQV}	RP# High to Output Delay			600	ns
t _{GLQV}	OE# to Output Delay	2		50	ns
t _{ELQX}	CE# to Output in Low Z	3	0		ns
t _{EHQZ}	CE# High to Output in High Z	3		50	ns
t _{GLQX}	OE# to Output in Low Z	3	0		ns
t _{GHQZ}	OE# High to Output in High Z	3		20	ns
t _{OH}	Output Hold from Address, CE# or OE# Change, Whichever Occurs First	3	0		ns
t _{FLQV} t _{FHQV}	BYTE# to Output Delay	3		120	ns
t _{FLQZ}	BYTE# to Output in High Z	3		30	ns
t _{ELFL} t _{ELFH}	CE# Low to BYTE# High or Low	3		5	ns

NOTE:

See 3.3V $\rm V_{CC}$ Read-Only Operations for notes 1 through 4.

 V_{CC} =3.3V±0.3V, T_A =-40°C to +85°C

	Versions ⁽⁴⁾		LH28F160)S3H-L100	
Sym.	Parameter	Notes	Min.	Max.	Unit
t _{AVAV}	Read Cycle Time		100		ns
t _{AVQV}	Address to Output Delay			100	ns
t _{ELQV}	CE# to Output Delay	2		100	ns
t _{PHQV}	RP# High to Output Delay			600	ns
t _{GLQV}	OE# to Output Delay	2		45	ns
t _{ELQX}	CE# to Output in Low Z	3	0		ns
t _{EHQZ}	CE# High to Output in High Z	3		50	ns
t _{GLQX}	OE# to Output in Low Z	3	0		ns
t _{GHQZ}	OE# High to Output in High Z	3		20	ns
t _{OH}	Output Hold from Address, CE# or OE# Change, Whichever Occurs First	3	0		ns
t _{FLQV}	BYTE# to Output Delay	3		100	ns
t _{FLQZ}	D)/TE#4 O 4 41 111 1 7			30	ns
t _{ELFL}	CE# Low to BYTE# High or Low	3		5	ns

- 1. See AC Input/Output Reference Waveform for maximum allowable input slew rate.
- 2. OE# may be delayed up to t_{ELQV} - t_{GLQV} after the falling edge of CE# without impact on t_{ELQV} .
- 3. Sampled, not 100% tested.
- 4. See Ordering Information for device speeds (valid operational combinations).






Figure 17. AC Waveform for Read Operations




Figure 18. BYTE# Timing Waveforms



6.2.5 AC CHARACTERISTICS - WRITE OPERATIONS(1)

 V_{CC} =2.7V-3.6V, T_{A} =-40°C to +85°C


	Versions ⁽⁵⁾		LH28F160	S3H-L120	
Sym.	Parameter	Notes	Min.	Max.	Unit
t _{AVAV}	Write Cycle Time		120		ns
t _{PHWL}	RP# High Recovery to WE# Going Low	2	1		μs
t _{ELWL}	CE# Setup to WE# Going Low		10		ns
t _{WLWH}	WE# Pulse Width		50		ns
t _{SHWH}	WP# V _{IH} Setup to WE# Going High	2	100		ns
t _{VPWH}	V _{PP} Setup to WE# Going High	2	100		ns
t _{AVWH}	Address Setup to WE# Going High	3	50		ns
t _{DVWH}			50		ns
t _{WHDX}	Data Hold from WE# High		5		ns
t _{WHAX}	Address Hold from WE# High		5		ns
t _{WHEH}	CE# Hold from WE# High		10		ns
t_{WHWL}	WE# Pulse Width High		30		ns
t _{WHRL}	WE# High to STS Going Low			100	ns
t _{WHGL}	Write Recovery before Read		0		ns
t _{QVVL}	\\\\\\\\\\\\\\\\\\\\\\\\\\\\\\\\\\\\\\		0	·	ns
t _{QVSL}			0		ns
t _{FVWH}	BYTE# Setup to WE# Going High		50		ns
t _{WHFV}	BYTE# Hold from WE# High		NOTE 6		ns

NOTE:

See 3.3V $\rm V_{CC}$ WE#-Controlled Writes for notes 1 through 6.

	Versions ⁽⁵⁾		LH28F160	S3H-L100	
Sym.	Parameter	Notes	Min.	Max.	Unit
t _{AVAV}	Write Cycle Time		100		ns
t _{PHWL}	RP# High Recovery to WE# Going Low	2	1		μs
t _{FLWL}	CE# Setup to WE# Going Low		10		ns
t _{WLWH}	WE# Pulse Width		50		ns
t _{SHWH}	WP# V _{IH} Setup to WE# Going High	2	100		ns
t _{VPWH}	V _{PP} Setup to WE# Going High	2	100		ns
t _{AVWH}	A Library Onto a WEW Onto a High		50		ns
t _{DVWH} Data Setup to WE# Going High		3	50		ns
t _{WHDX}	Data Hold from WE# High		5		ns
t _{WHAX}	Address Hold from WE# High		5		ns
t _{WHEH}	CE# Hold from WE# High		10		ns
t _{WHWL}	WE# Pulse Width High		30		ns
t _{WHRL}	. NATE (1.11) 1 OTO O : 1			100	ns
t _{WHGL}	4 Maita Danassams kafana Danal		0		ns
t _{QVVL} V _{PP} Hold from Valid SRD, STS High Z		2,4	0		ns
t _{QVSL}	AMDUAL HALLOW A VALUEDDD OTO LUAL 7		0		ns
t _{EVWH}	BYTE# Setup to WE# Going High		50		ns
t _{WHFV}	BYTE# Hold from WE# High		NOTE 6		ns

- Read timing characteristics during block erase, full chip erase, (multi) wrod/byte write and block lock-bit configuration operations are the same as during read-only operations. Refer to AC Characteristics for read-only operations.
- 2. Sampled, not 100% tested.
- 3. Refer to Table 4 for valid A_{IN} and D_{IN} for block erase, full chip erase, (multi) word/byte write or block lock-bit configuration.
- 4. V_{PP} should be held at $V_{PPH1/2/3}$ until determination of block erase, full chip erase, (multi) word/byte write or block lock-bit configuration success (SR.1/3/4/5=0).
- 5. See Ordering Information for device speeds (valid operational combinations).
- 6. BYTE# should be in stable until determination of block erase, full chip erase, (multi) word/byte write, block lock-bit configuration or STS configuration success (SR.7=1).



- 1. V_{CC} power-up and standby.
- 2. Write each setup command.
- 3. Write each confirm command or valid address and data.
- 4. Automated erase or program delay.
- 5. Read status register data.
- 6. Write Read Array command.
- 7. CE# is defined as the latter of CE₀# and CE₁# going Low or the first of CE₀# or CE₁# going High.

Figure 19. AC Waveform for WE#-Controlled Write Operations



6.2.6 ALTERNATIVE CE#-CONTROLLED WRITES(1)

 V_{CC} =2.7V-3.6V, T_{A} =-40°C to +85°C

	Versions ⁽⁵⁾		LH28F160	S3H-L120	
Sym.	Parameter	Notes	Min.	Max.	Unit
t _{AVAV}	Write Cycle Time		120		ns
t _{PHEL}	RP# High Recovery to CE# Going Low	2	1		μs
t _{WLEL}	WE# Setup to CE# Going Low		0		ns
t _{ELEH}	CE# Pulse Width		70		ns
t _{SHEH}	WP# V _{IH} Setup to CE# Going High	2	100		ns
t _{VPEH}	V _{PP} Setup to CE# Going High	2	100		ns
t _{AVEH}	Address Setup to CE# Going High	3	50		ns
t _{DVEH}	Data Setup to CE# Going High	3	50		ns
t _{EHDX}	Data Hold from CE# High		5		ns
t _{EHAX}	Address Hold from CE# High		5		ns
t _{EHWH}	WE# Hold from CE# High		0		ns
t _{EHEL}	CE# Pulse Width High		25		ns
t _{EHRL}	CE# High to STS Going Low			100	ns
t _{EHGL}	Write Recovery before Read		0		ns
t _{QVVL}	1)/ 11 11/		0		ns
t _{QVSL}	11/5		0		ns
t _{FVEH}	BYTE# Setup to CE# Going HIgh		50		ns
t _{EHFV}	BYTE# Hold from CE# High		NOTE 6		ns


NOTE:

See 3.3V $\rm V_{CC}$ Alternative CE#-Controlled Writes for notes 1 through 6.

	Versions ⁽⁵⁾		LH28F160	S3H-L100	
Sym.	Parameter	Notes	Min.	Max.	Unit
t _{AVAV}	Write Cycle Time		100		ns
t _{PHFI}	RP# High Recovery to CE# Going Low	2	1		μs
t _{WLEL}	WE# Setup to CE# Going Low		0		ns
t _{ELEH}	CE# Pulse Width		70		ns
t _{SHEH}	WP# V _{IH} Setup to CE# Going High	2	100		ns
t _{VPEH}	V _{PP} Setup to CE# Going High	2	100		ns
t _{AVEH}			50		ns
t _{DVEH}	M*E''		50		ns
t _{EHDX}	Data Hold from CE# High		5		ns
t _{EHAX}	Address Hold from CE# High		5		ns
t _{EHWH}	WE# Hold from CE# High		0		ns
t _{EHEL}	CE# Pulse Width High		25		ns
t _{EHRL}	CE# High to STS Going Low			100	ns
t _{EHGL}			0		ns
t _{QVVL}	. \		0		ns
t _{QVSL}			0		ns
t _{FVEH}	BYTE# Setup to CE# Going High		50		ns
t _{EHFV}	BYTE# Hold from CE# High		NOTE 6		ns

- 1. In systems where CE# defines the write pulse width (within a longer WE# timing waveform), all setup, hold and inactive WE# times should be measured relative to the CE# waveform.
- 2. Sampled, not 100% tested.
- 3. Refer to Table 4 for valid A_{IN} and D_{IN} for block erase, full chip erase, (multi) word/byte write or block lock-bit configuration.
- 4. V_{PP} should be held at $V_{PPH1/2/3}$ until determination of block erase, full chip erase, (multi) word/byte write or block lock-bit configuration success (SR.1/3/4/5=0).
- 5. See Ordering Information for device speeds (valid operational combinations).
- 6. BYTE# should be in stable until determination of block erase, full chip erase, (multi) word/byte write, block lock-bit configuration or STS configuration success (SR.7=1).





- V_{CC} power-up and standby.
 Write each setup command.
- 3. Write each confirm command or valid address and data.
- 4. Automated erase or program delay.
- 5. Read status register data.
- 6. Write Read Array command.
- 7. CE# is defined as the latter of CE $_0$ # and CE $_1$ # going Low or the first of CE $_0$ # or CE $_1$ # going High.

Figure 20. AC Waveform for CE#-Controlled Write Operations



6.2.7 RESET OPERATIONS




Figure 21. AC Waveform for Reset Operation

Reset AC Specifications

	Neset A	o opcom	loutions				
	V _{CC} =2.7V		V _{CC} =				
Symbol	Parameter	Notes	Min.	Max.	Min.	Max.	Unit
t _{PLPH}	RP# Pulse Low Time						
	(If RP# is tied to V_{CC} , this specification is		100		100		ns
	not applicable)						
t _{PLRH}	RP# Low to Reset during Block Erase,						
	Full Chip Erase, (Multi) Word/Byte Write	1,2		21.5		21.1	μs
	or Block Lock-Bit Configuration						
t _{23VPH}	V _{CC} at 2.7V to RP# High	2	100		100		nc
	V _{CC} at 3.0V to RP# High	3	100		100		ns

- 1. If RP# is asserted while a block erase, full chip erase, (multi) word/byte write or block lock-bit configuration operation is not executing, the reset will complete within 100ns.
- A reset time, t_{PHQV}, is required from the latter of STS going High Z or RP# going high until outputs are valid.
 When the device power-up, holding RP# low minimum 100ns is required after V_{CC} has been in predefined range and also has been in stable there.



6.2.8 BLOCK ERASE, FULL CHIP ERASE, (MULTI) WORD/BYTE WRITE AND BLOCK LOCK-BIT CONFIGURATION PERFORMANCE⁽³⁾

 V_{CC} =2.7V-3.6V, T_{A} =-40°C to +85°C

		- CC	, - <u>-</u>							
				7V-3.6V		0V-3.6V		5V-5.5V		
Sym.	Parameter	Notes	Typ.(1)	Max.	Typ. ⁽¹⁾	Max.	Typ. ⁽¹⁾	Max.	Unit	
t _{WHQV1}	Word/Byte Write Time (using W/B write, in word mode)	2	22.19	250	22.19	250	13.2	180	μs	
t _{WHQV1} t _{EHQV1}	Word/Byte Write Time (using W/B write, in byte mode)	2	19.9	250	19.9	250	13.2	180	μs	
	Word/Byte Write Time (using multi word/byte write)	2	5.76	250	5.76	250	2.76	180	μs	
	Block Write Time (using W/B write, in word mode)	2	0.73	8.2	0.73	8.2	0.44	4.8	S	
	Block Write Time (using W/B write, in byte mode)	2	1.31	16.5	1.31	16.5	0.87	10.9	S	
	Block Write Time (using multi word/byte write)	2	0.37	4.1	0.37	4.1	0.18	2	S	
t_{WHQV2} t_{EHQV2}	Block Erase Time	2	0.56	10	0.56	10	0.42	10	s	
	Full Chip Erase Time		17.9	320	17.9	320	13.4	320	S	
t _{WHQV3}	Set Block Lock-Bit Time	2	22.17	250	22.17	250	13.2	180	μs	
t _{WHQV4}	Clear Block Lock-Bits Time	2	0.56	10	0.56	10	0.42	10	s	
t _{WHRH1}	Write Suspend Latency Time to Read		7.24	10.2	7.24	10.2	6.73	9.48	μs	
t _{WHRH2}	Erase Suspend Latency Time to Read		15.5	21.5	15.5	21.5	12.54	17.54	μs	

NOTE:

See 3.3V V_{CC} Block Erase, Full Chip Erase, (Multi) Word/Byte Write and Block Lock-Bit Configuration Performance for notes 1 through 3.

V _{CC} =3.3V±	$0.3V$, $T_A = -40^{\circ}C$ to $+85^{\circ}C$


			V _{PP} =3.0V-3.6V		V _{PP} =4.5V-5.5V		
Sym.	Parameter	Notes	Typ. ⁽¹⁾	Max.	Typ. ⁽¹⁾	Max.	Unit
t _{WHQV1}	Word/Byte Write Time (using W/B write, in word mode)	2	21.75	250	12.95	180	μs
t _{WHQV1}	Word/Byte Write Time (using W/B write, in byte mode)	2	19.51	250	12.95	180	μs
	Word/Byte Write Time (using multi word/byte write)	2	5.66	250	2.7	180	μs
	Block Write Time (using W/B write, in word mode)	2	0.72	8.2	0.43	4.8	S
	Block Write Time (using W/B write, in byte mode)	2	1.28	16.5	0.85	10.9	s
	Block Write Time (using multi word/byte write)	2	0.36	4.1	0.18	2	s
t _{WHQV2}	Block Erase Time	2	0.55	10	0.41	10	s
	Full Chip Erase Time		17.6	320	13.1	320	S
t _{WHQV3}	Set Block Lock-Bit Time	2	21.75	250	12.95	180	μs
t _{WHQV4}	Clear Block Lock-Bits Time	2	0.55	10	0.41	10	s
t _{WHRH1}	Write Suspend Latency Time to Read		7.1	10	6.6	9.3	μs
t _{WHRH2}	Erase Suspend Latency Time to Read		15.2	21.1	12.3	17.2	μs

- Typical values measured at T_A=+25°C and nominal voltages. Assumes corresponding block lock-bits are not set. Subject to change based on device characterization.
 Excludes system-level overhead.
 Sampled but not 100% tested.



7 ADDITIONAL INFORMATION

7.1 Ordering Information



		Valid Operational Combinations			
		V _{CC} =2.7V-3.6V	V _{CC} =3.3V±0.3V		
		50pF load,	50pF load,		
Option	Order Code	1.35V I/O Levels	1.5V I/O Levels		
1	LH28F160S3HNS-TV	LH28F160S3H-L120	LH28F160S3H-L100		



8 Package and packing specification

[Applicability]

This specification applies to IC package of the LEAD-FREE delivered as a standard specification.

1. Storage Conditions.

- 1-1. Storage conditions required before opening the dry packing.
 - Normal temperature : 5~40°C
 - Normal humidity: 80%(Relative humidity) max.
 - *"Humidity" means "Relative humidity"

1-2. Storage conditions required after opening the dry packing.

In order to prevent moisture absorption after opening, ensure the following storage conditions apply:

- (1) Storage conditions for one-time soldering. (Convection reflow*1, IR/Convection reflow.*1, or Manual soldering.)
 - Temperature : 5~25°C
 - · Humidity: 60% max.
 - · Period: 72 hours max. after opening.
- (2) Storage conditions for two-time soldering. (Convection reflow.*1, IR/Convection reflow.*1)
 - a. Storage conditions following opening and prior to performing the 1st reflow.
 - Temperature : 5~25°C
 - · Humidity: 60% max.
 - Period: 72 hours max. after opening.
 - b. Storage conditions following completion of the 1st reflow and prior to performing the 2nd reflow.
 - Temperature : 5~25°C
 - Humidity: 60% max.
 - Period: 72 hours max. after completion of the 1st reflow.


1-3. Temporary storage after opening.

To re-store the devices before soldering, do so only once and use a dry box or place desiccant (with a blue humidity indicator) with the devices and perform dry packing again using heat-sealing.

The storage period, temperature and humidity must be as follows:

(1) Storage temperature and humidity.

※1: External atmosphere temperature and humidity of the dry packing.



- (2) Storage period.
 - X1+X2: Refer to Section 1-2(1) and (2)a, depending on the mounting method.
 - Y : Two weeks max.

^{*1:} Air or nitrogen environment.



2. Baking Condition.

- (1) Situations requiring baking before mounting.
 - Storage conditions exceed the limits specified in Section 1-2 or 1-3.
 - · Humidity indicator in the desiccant was already red (pink) when opened.
 - (Also for re-opening.)
- (2) Recommended baking conditions.
 - · Baking temperature and period :

120°C for $16\sim24$ hours.

- The above baking conditions apply since the trays are heat-resistant.
- (3) Storage after baking.
 - After baking, store the devices in the environment specified in Section 1-2 and mount immediately.
- 3. Surface mount conditions.

The following soldering condition are recommended to ensure device quality.

- 3-1. Soldering.
- (1) Convection reflow or IR/Convection. (one-time soldering or two-time soldering in air or nitrogen environment)
 - · Temperature and period :

A) Peak temperature.

250°C max.

B) Heating temperature.

40 to 60 seconds as 220°C


C) Preheat temperature.

It is 150 to 200°C, and is 120±30 seconds

D) Temperature increase rate.

It is 1 to 3°C/seconds

- Measuring point : IC package surface.
- · Temperature profile:



SHARP

(2) Manual soldering (soldering iron) (one-time soldering only)

Soldering iron should only touch the IC's outer leads.

· Temperature and period:

350°C max. for 3 seconds / pin max.

(Soldering iron should only touch the IC's outer leads.)

· Measuring point : Soldering iron tip.

4. Condition for removal of residual flux.

(1) Ultrasonic washing power: 25 watts / liter max.

(2) Washing time: Total 1 minute max.

(3) Solvent temperature : $15\sim40^{\circ}$ C

5. Package outline specification.

Refer to the attached drawing.

(Plastic body dimensions do not include burr of resin.)

The contents of LEAD-FREE TYPE application of the specifications. (*2)

6. Markings.

6-1. Marking details. (The information on the package should be given as follows.)

(1) Product name : LH28F160S3HNS-TV

(2) Company name : SHARP

(3) Date code : (Example) YYWW XXX

YY \rightarrow Denotes the production year. (Last two digits of the year.) WW \rightarrow Denotes the production week. $(01 \cdot 02 \cdot \sim \cdot 52 \cdot 53)$

XXX \rightarrow Denotes the production ref. code (1 \sim 3 digits).

(4) "JAPAN" indicates the country of origin.

6-2. Marking layout.

The layout is shown in the attached drawing.


(However, this layout does not specify the size of the marking character and marking position.)


*2 The contents of LEAD-FREE TYPE application of the specifications.


LEAD FINISH or BALL TYPE	LEAD-FREE TYPE (Sn-Bi)
DATE CODE	They are those with an underline.
The word of "LEAD FREE" is printed on the packing label	Printed




(Note) It is those with an underline printing in a date code because of a LEAD-FREE type.







DETAIL A



SSOP056-P-0600-AA2021

I E A	D TVDE	LEAD FINISH			LEAD MATERIAL		
LEAD TYPE		Sn-Bi PLATING		ATING	Cu		
NAME	SSOP056	-P-0600	-	NOTE : Plastic body dim	ensions do not include burr of resin.		
DRAWING N	A A 2021	INIT					



7. Packing Specifications (Dry packing for surface mount packages.)

7-1. Packing materials.

Material name	Material specifications	Purpose	
Inner carton	Cardboard (500 devices / inner carton	Packing the devices.	
	max.)	(10 trays / inner carton)	
Tray	Conductive plastic (50 devices / tray)	Securing the devices.	
Upper cover tray	Conductive plastic (1 tray / inner carton)	Securing the devices.	
Laminated aluminum	Aluminum polyethylene	Keeping the devices dry.	
bag			
Desiccant	Silica gel	Keeping the devices dry.	
Label	Paper	Indicates part number,	
		quantity, and packed date.	
PP band	Polypropylene (3 pcs. / inner carton)	Securing the devices.	
Outer carton	Cardboard (2000 devices / outer carton	Outer packing.	
	max.)		

(Devices must be placed on the tray in the same direction.)

7-2. Outline dimension of tray.

Refer to the attached drawing.


7-3. Outline dimension of carton.

Refer to the attached drawing.


- 8. Precautions for use.
 - (1) Opening must be done on an anti-ESD treated workbench.
 All workers must also have undergone anti-ESD treatment.
 - (2) The trays have undergone either conductive or anti-ESD treatment.


 If another tray is used, make sure it has also undergone conductive or anti-ESD treatment.
 - (3) The devices should be mounted within one year of the date of delivery.


















Flash memory LHFXXKXX family Data Protection

Noises having a level exceeding the limit specified in the specification may be generated under specific operating conditions on some systems.

Such noises, when induced onto WE# signal or power supply, may be interpreted as false commands, causing undesired memory updating.

To protect the data stored in the flash memory against unwanted overwriting, systems operating with the flash memory should have the following write protect designs, as appropriate:

1) Protecting data in specific block

Setting the lock bit of the desired block and pulling WP# low disables the writing operation on that block. By using this feature, the flash memory space can be divided into, for example, the program section(locked section) and data section(unlocked section).

By controlling WP#, desired blocks can be locked/unlocked through the software. For further information on setting/resetting block bit, refer to the specification. (See chapter 4.12 and 4.13.)

2) Data protection through Vpp

When the level of Vpp is lower than VPPLK (lockout voltage), write operation on the flash memory is disabled. All blocks are locked and the data in the blocks are completely write protected.

For the lockout voltage, refer to the specification. (See chapter 6.2.3.)

3) Data protection through RP#

When the RP# is kept low during power up and power down sequence such as voltage transition, write operation on the flash memory is disabled, write protecting all blocks.


For the details of RP# control, refer to the specification. (See chapter 5.6 and 6.2.7.)



A-1 RECOMMENDED OPERATING CONDITIONS

A-1.1 At Device Power-Up

AC timing illustrated in Figure A-1 is recommended for the supply voltages and the control signals at device power-up. If the timing in the figure is ignored, the device may not operate correctly.



- *1 t_{5VPH} for the device in 5V operations.
- *2 To prevent the unwanted writes, system designers should consider the V_{CCW} (V_{PP}) switch, which connects V_{CCW} (V_{PP}) to GND during read operations and $V_{CCWH1/2}$ ($V_{PPH1/2}$) during write or erase operations. See the application note AP-007-SW-E for details.

Figure A-1. AC Timing at Device Power-Up

For the AC specifications t_{VR} , t_R , t_F in the figure, refer to the next page. See the "ELECTRICAL SPECIFICATIONS" described in specifications for the supply voltage range, the operating temperature and the AC specifications not shown in the next page.

- · · · ·



A-1.1.1 Rise and Fall Time

Symbol	Parameter	Notes	Min.	Max.	Unit
t_{VR}	V _{CC} Rise Time	1	0.5	30000	μs/V
t _R	Input Signal Rise Time	1, 2		1	μs/V
t _F	Input Signal Fall Time	1, 2		1	μs/V

- 1. Sampled, not 100% tested.
- 2. This specification is applied for not only the device power-up but also the normal operations. $t_R(Max.)$ and $t_F(Max.)$ for RP# (RST#) are $100\mu s/V$.



A-1.2 Glitch Noises

Do not input the glitch noises which are below V_{IH} (Min.) or above V_{IL} (Max.) on address, data, reset, and control signals, as shown in Figure A-2 (b). The acceptable glitch noises are illustrated in Figure A-2 (a).




Figure A-2. Waveform for Glitch Noises

See the "DC CHARACTERISTICS" described in specifications for V_{IH} (Min.) and V_{IL} (Max.).



A-2 RELATED DOCUMENT INFORMATION⁽¹⁾

Document No.	Document Name
AP-001-SD-E	Flash Memory Family Software Drivers
AP-006-PT-E	Data Protection Method of SHARP Flash Memory
AP-007-SW-E	RP#, V _{PP} Electric Potential Switching Circuit

NOTE:

 International customers should contact their local SHARP or distribu- 	ution sal	les offic
-------------------------------------------------------------------------------------------	-----------	-----------

SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE.

Suggested applications (if any) are for standard use; See Important Restrictions for limitations on special applications. See Limited Warranty for SHARP's product warranty. The Limited Warranty is in lieu, and exclusive of, all other warranties, express or implied. ALL EXPRESS AND IMPLIED WARRANTIES, INCLUDING THE WARRANTIES OF MERCHANTABILITY, FITNESS FOR USE AND FITNESS FOR A PARTICULAR PURPOSE, ARE SPECIFICALLY EXCLUDED. In no event will SHARP be liable, or in any way responsible, for any incidental or consequential economic or property damage.



NORTH AMERICA

Fast Info: (1) 800-833-9437

www.sharpsma.com

SHARP Microelectronics of the Americas 5700 NW Pacific Rim Blvd. Camas, WA 98607, U.S.A. Phone: (1) 360-834-2500 Fax: (1) 360-834-8903

TAIWAN

SHARP Electronic Components (Taiwan) Corporation 8F-A, No. 16, Sec. 4, Nanking E. Rd. Taipei, Taiwan, Republic of China Phone: (886) 2-2577-7341 Fax: (886) 2-2577-7326/2-2577-7328

CHINA

SHARP Microelectronics of China (Shanghai) Co., Ltd.
28 Xin Jin Qiao Road King Tower 16F Pudong Shanghai, 201206 P.R. China Phone: (86) 21-5854-7710/21-5834-6056 Fax: (86) 21-5854-4340/21-5834-6057 **Head Office:**

No. 360, Bashen Road, Xin Development Bldg. 22 Waigaoqiao Free Trade Zone Shanghai 200131 P.R. China Email: smc@china.global.sharp.co.jp

EUROPE

SHARP Microelectronics Europe Division of Sharp Electronics (Europe) GmbH Sonninstrasse 3 20097 Hamburg, Germany Phone: (49) 40-2376-2286 Fax: (49) 40-2376-2232 www.sharpsme.com

SINGAPORE

SHARP Electronics (Singapore) PTE., Ltd. 438A, Alexandra Road, #05-01/02 Alexandra Technopark, Singapore 119967 Phone: (65) 271-3566 Fax: (65) 271-3855

HONG KONG

SHARP-ROXY (Hong Kong) Ltd. 3rd Business Division, 17/F, Admiralty Centre, Tower 1 18 Harcourt Road, Hong Kong Phone: (852) 28229311 Fax: (852) 28660779 www.sharp.com.hk Shenzhen Representative Office:

Room 13B1, Tower C, Electronics Science & Technology Building Shen Nan Zhong Road Shenzhen, P.R. China

Phone: (86) 755-3273731 Fax: (86) 755-3273735

JAPAN

SHARP Corporation Electronic Components & Devices 22-22 Nagaike-cho, Abeno-Ku Osaka 545-8522, Japan Phone: (81) 6-6621-1221 Fax: (81) 6117-725300/6117-725301 www.sharp-world.com

KOREA

SHARP Electronic Components (Korea) Corporation RM 501 Geosung B/D, 541 Dohwa-dong, Mapo-ku Seoul 121-701, Korea Phone: (82) 2-711-5813 ~ 8 Fax: (82) 2-711-5819