

**Harvatek Surface Mount LEDs Data Sheet**  
**F10Q1FH--20P000742U1930**

Official Product	HT Part No. F10Q1FH--20P000742U1930			
Tentative Product	*****	*****		
Specifications are subject to changes for improvement without advance notice. Proprietary data, drawings, company confidential all rights reserved.		11/20/2024	Version 1.0	Page 1/16

<b>DISCLAIMER.....</b>	<b>3</b>
LIFE SUPPORT POLICY .....	3
<b>PRODUCT SPECIFICATION.....</b>	<b>4</b>
ATTENTION: ELECTROSTATIC DISCHARGE (ESD) PROTECTION .....	4
<b>LABEL SPECIFICATIONS: .....</b>	<b>5</b>
<b>SPECIFICATIONS RANGE. ....</b>	<b>6</b>
<b>CHROMATICITY COORDINATE:.....</b>	<b>7</b>
<b>PRODUCT FEATURES .....</b>	<b>8</b>
<b>ELECTRO-OPTICAL CHARACTERISTICS.....</b>	<b>8</b>
<b>PACKAGE OUTLINE DIMENSION AND RECOMMENDED SOLDERING PATTERN FOR REFLOW SOLDERING .....</b>	<b>8</b>
ABSOLUTE MAXIMUM RATINGS .....	8
CHARACTERISTICS OF F10Q1FH.....	9
<b>PRECAUTION FOR USE .....</b>	<b>10</b>
<b>PACKAGING .....</b>	<b>11</b>
TAPE DIMENSION .....	11
REEL DIMENSION .....	12
PACKING .....	12
DRY PACK .....	13
BAKING .....	13
PRECAUTIONS .....	13
<b>HANDLING OF SILICONE RESIN LEDS.....</b>	<b>14</b>
<b>REFLOW SOLDERING .....</b>	<b>15</b>
REWORKING .....	15
CLEANING .....	15
<b>REVISION HISTORY .....</b>	<b>16</b>

Official Product	HT Part No. F10Q1FH--20P000742U1930		
Tentative Product	*****	*****	
Specifications are subject to changes for improvement without advance notice. Proprietary data, drawings, company confidential all rights reserved.	11/20/2024	Version 1.0	Page 2/16

## DISCLAIMER

HARVATEK reserves the right to make changes without further notice to any products herein to improve reliability, function or design. HARVATEK does not assume any liability arising out of the application or use of any product or circuit described herein; neither does it convey any license under its patent rights, nor the rights of others.

## Life Support Policy

HARVATEK's products are not authorized for use as critical components in life support devices or systems without the express written approval of the President of HARVATEK or HARVATEK INTERNATIONAL. As used herein:

1. Life support devices or systems are devices or systems which, (a) are intended for surgical implant into the body, or (b) support or sustain life, and (c) whose failure to perform when properly used in accordance with instructions for use provided in the labeling, can be reasonably expected to result in a significant injury of the user.
2. A critical component in any component of a life support device or system whose failure to perform can be reasonably expected to cause the failure of the life support device or system, or to affect its safety or effectiveness.

Official Product	HT Part No. F10Q1FH--20P000742U1930		
Tentative Product	*****	*****	
Specifications are subject to changes for improvement without advance notice. Proprietary data, drawings, company confidential all rights reserved.	11/20/2024	Version 1.0	Page 3/16

## Product Specification

Item	Specification	Material	Quantity
Luminous Intensity(Iv)	3020-3600 mcd @20mA/ T <sub>S</sub> = 25°C ;Tolerance:±10%		
Chromaticity Coordinate	As page 6 & 7 @20mA/ T <sub>S</sub> = 25°C ;Tolerance:±0.005		
Vf	2.7-3.1 V @20mA/ T <sub>S</sub> = 25°C ;Tolerance:±0.05V		
Ir	< 10 μA @ V <sub>R</sub> = 5 V		
Resin	Yellow	Silicone Resin	
Carrier tape	According to EIA 481-1A specs	Conductive black tape	2000pcs per reel
Reel	According to EIA 481-1A specs	Conductive black	
Label	HT standard		
Packing bag	250x230mm	Aluminum laminated bag/ no-zipper	One reel one bag
Carton	HT standard	Paper	Non-specified

### Others:

Each immediate box consists of 5 reels. The 5 reels may not necessarily have the same lot number or the same bin combinations of Iv, CIE and Vf. Each reel has a label identifying its specification; the immediate box consists of a product label as well.

Note :This is shipped test conditions

※Remarks: This product should be operated in forward bias. If a reverse voltage is continuously applied to the product, such operation can cause migration resulting in LED damage.

### ATTENTION: Electrostatic Discharge (ESD) protection




The symbol to the left denotes that ESD precaution is needed. ESD protection for GaP and AlGaAs based chips is necessary even though they are relatively safe in the presence of low static-electric discharge. Parts built with AlGaInP, GaN, or/and InGaN based chips are **STATIC SENSITIVE devices**. ESD precaution must be taken during design and assembly.

If manual work or processing is needed, please ensure the device is adequately protected from ESD during the process.

Official Product	HT Part No. F10Q1FH--20P000742U1930		
Tentative Product	*****	*****	
Specifications are subject to changes for improvement without advance notice. Proprietary data, drawings, company confidential all rights reserved.	11/20/2024	Version 1.0	Page 4/16

## Label Specifications:



### ■ Harvatek P/N

**F                      10Q                      1                      FH--                      20P-                      0007                      42**

Product	Package	Dice Qty	Color	Current	Series Number	Taping
LF	3.8(L)x1.0(W)x0.6(H) mm	1:Single	FH:White	20mA	X001~XZZZ	1.Taping style 2. Qty

### ■ Lot No.:

1	2	3	4	5	6	7	8	9	10
<b>E</b>	<b>1</b>	<b>A</b>	<b>1</b>	<b>A</b>	<b>2</b>	<b>2</b>	<b>L</b>	<b>1</b>	<b>2</b>
Code 1 2		Code 3	Code 4	Code 5	Code 6	Code 7	Code 8	Code 9	Code 10
		Mfg. Year	Mfg. Month	Mfg. Date	Consecutive number		Special code		
Internal Tracing Code		2020-L	1:Jan. 2:Feb. ... A:Oct. B:Nov. C:Dec.	1:A	01~ZZ		000~ZZZ		
		2021-M		2:B					
		2022-P		3:C					
		2023-Q		...					
		...		26:Z					
		2026-T		27:7					
		2027-V		28:8					
		...		29:9					
		2030-Y		30:3					
		2031-Z		31:4					
		...							

Official Product	HT Part No. F10Q1FH--20P000742U1930		
Tentative Product	*****	*****	
Specifications are subject to changes for improvement without advance notice. Proprietary data, drawings, company confidential all rights reserved.	11/20/2024	Version 1.0	Page 5/16

## Specifications Range.

### ■ Luminous Intensity (lv) Bin:

Color	Bin Code	Spec. Range
FH	Z92	3020-3200 mcd
	ZA1	3200-3400 mcd
	ZA2	3400-3600 mcd

Note: It maintains a tolerance of  $\pm 10\%$  on luminous intensity


### ■ Color Bin:

	X	Y
FEA	0.2820	0.2700
	0.2740	0.2560
	0.2800	0.2480
	0.2880	0.2620
FHA	0.2900	0.2840
	0.2820	0.2700
	0.2880	0.2620
	0.2960	0.2760
FIA	0.2980	0.2980
	0.2900	0.2840
	0.2960	0.2760
	0.3040	0.2900

Note: It maintains a tolerance of x, y  $\pm 0.005$

Official Product	HT Part No. F10Q1FH--20P000742U1930			
Tentative Product	*****	*****		
Specifications are subject to changes for improvement without advance notice. Proprietary data, drawings, company confidential all rights reserved.		11/20/2024	Version 1.0	Page 6/16

**Chromaticity Coordinate:**



■ **Forward Voltage (Vf) Bin:**

Color	Bin Code	Spec. Range
FH	G4	2.7-2.8 V
	H1	2.8-2.9 V
	H2	2.9-3.0 V
	H3	3.0-3.1 V

Note: It maintains a tolerance of  $\pm 0.05V$  on forward voltage measurements

Official Product	HT Part No. F10Q1FH--20P000742U1930			
Tentative Product	*****	*****		
Specifications are subject to changes for improvement without advance notice. Proprietary data, drawings, company confidential all rights reserved.		11/20/2024	Version 1.0	Page 7/16

## Product Features

### Electro-Optical Characteristics

(T<sub>Soldering</sub> ,25 °C)

Series	Emitting Color	Material	V <sub>F</sub> (V)		Chromaticity Coordinate x,y	I <sub>V</sub> (mcd) Typical	Viewing Angle $2\theta \frac{1}{2}$
			typ	max			
F10Q1FH--20	FH	InGaN	2.9	3.1	x=0.2880 ,y=0.2720	3250	120

### Package Outline Dimension and Recommended Soldering Pattern for Reflow Soldering

(Unit:mm Tolerance: +/-0.1)

Outline Dim.	Suggest Soldering Pattern
Soldering terminals may shift in the x, y direction.	

### Absolute Maximum Ratings


Series	P <sub>D</sub> (mW)	I <sub>F</sub> (mA)	I <sub>FP</sub> (mA)*	T <sub>OP</sub> (°C)	T <sub>ST</sub> (°C)
Color	Power Dissipation	Forward Current	Pulse Forward Current	Operating Temperature	Storage Temperature
FH	93	30	35	-40~+85	-40~+100

\* Condition for I<sub>FP</sub> is pulse of 1/10 duty and 0.1msec width

Official Product	HT Part No. F10Q1FH--20P000742U1930		
Tentative Product	*****	*****	
Specifications are subject to changes for improvement without advance notice. Proprietary data, drawings, company confidential all rights reserved.	11/20/2024	Version 1.0	Page 8/16



## Characteristics of F10Q1FH



Official Product	HT Part No. F10Q1FH--20P000742U1930		
Tentative Product	*****	*****	
Specifications are subject to changes for improvement without advance notice. Proprietary data, drawings, company confidential all rights reserved.	11/20/2024	Version 1.0	Page 9/16

## Precaution for Use


1. The chips should not be used directly in any type of fluid such as water, oil, organic solvent, etc.
2. When the LEDs are illuminating, the maximum ambient temperature should be first considered before operation.
3. LEDs must be stored in a clean environment. A sealed container with a nitrogen atmosphere is necessary if the storage period is over 3 months after shipping.
4. The LEDs must be used within 4 weeks after unpacked. Unused products must be repacked in an anti-electrostatic package, folded to close any opening and then stored in a dry and cool space.
5. The appearance and specifications of the products may be modified for improvement without further notice.
6. The LEDs are sensitive to the static electricity and surge. It is strongly recommended to use a grounded wrist band and anti-electrostatic glove when handling the LEDs. If a voltage over the absolute maximum rating is applied to LEDs, it will damage LEDs. Damaged LEDs will show some abnormal characteristics such as remarkable increase of leak current, lower turn-on voltage and getting unlit at low current.

Official Product	HT Part No. F10Q1FH--20P000742U1930		
Tentative Product	*****	*****	
Specifications are subject to changes for improvement without advance notice. Proprietary data, drawings, company confidential all rights reserved.	11/20/2024	Version 1.0	Page 10/16


## Packaging

### Tape Dimension

#### Side View




Dim. A	Dim. B	Dim. C	Qty/Reel
$4.0 \pm 0.10$	$1.25 \pm 0.10$	$0.72 \pm 0.10$	2K




Official Product	HT Part No. F10Q1FH--20P000742U1930		
Tentative Product	*****	*****	
Specifications are subject to changes for improvement without advance notice. Proprietary data, drawings, company confidential all rights reserved.	11/20/2024	Version 1.0	Page 11/16

## Reel Dimension



## Packing



5 or 10 boxes per carton is available depending on shipment quantity.


Official Product	HT Part No. F10Q1FH--20P000742U1930			
Tentative Product	*****	*****		
Specifications are subject to changes for improvement without advance notice. Proprietary data, drawings, company confidential all rights reserved.		11/20/2024	Version 1.0	Page 12/16

## Dry Pack

All SMD optical devices are **MOISTURE SENSITIVE**. Avoid exposure to moisture at all times during transportation or storage. Every reel is packaged in a moisture protected anti-static bag. Each bag is properly sealed prior to shipment.

A humidity indicator will be included in the moisture protected anti-static bag prior to shipment.

The packaging sequence is as follows:



## Baking

It's recommended to bake before soldering once the pack is unsealed open & re-sealed after 4 weeks. The conditions are as followings:

1.  $60 \pm 3^{\circ}\text{C} \times (12 \sim 24\text{hrs})$  and  $< 5\% \text{ RH}$ , taped reel type
2.  $100 \pm 3^{\circ}\text{C} \times (45\text{min} \sim 1\text{hr})$ , bulk type
3.  $130 \pm 3^{\circ}\text{C} \times (15 \sim 30\text{min})$ , bulk type

## Precautions

1. Avoid exposure to moisture at all times during transportation or storage.
2. Anti-Static precaution must be taken when handling GaN, InGaN, and AlGaInP products.
3. It is suggested to connect the unit with a current limiting resistor of the proper size. Avoid applying a reverse voltage beyond the specified limit.
4. Avoid operation beyond the limits as specified by the absolute maximum ratings.
5. Avoid direct contact with the surface through which the LED emits light.
6. If possible, assemble the unit in a clean room or dust-free environment.

Official Product	HT Part No. F10Q1FH--20P000742U1930		
Tentative Product	*****	*****	
Specifications are subject to changes for improvement without advance notice. Proprietary data, drawings, company confidential all rights reserved.	11/20/2024	Version 1.0	Page 13/16

## Handling of Silicone Resin LEDs

### Handling Indications

During processing, mechanical stress on the surface should be minimized as much as possible.

Sharp objects of all types should not be used to pierce the sealing compound.



Figure 1

In general, LEDs should only be handled from the side. By the way, this also applies to LEDs without a silicone sealant, since the surface can also become scratched.




Figure 2

When populating boards in SMT production, there are basically no restrictions regarding the form of the pick and place nozzle, except that mechanical pressure on the surface of the resin must be prevented.

This is assured by choosing a pick and place nozzle which is larger than LEDs reflector area.


Official Product	HT Part No. F10Q1FH--20P000742U1930			
Tentative Product	*****	*****		
Specifications are subject to changes for improvement without advance notice. Proprietary data, drawings, company confidential all rights reserved.		11/20/2024	Version 1.0	Page 14/16

## Reflow Soldering

Recommend soldering paste specifications:

1. Operating temp.: Above 217 °C ,60~150sec
2. Peak temp.:260 °CMax.,10sec Max.
3. Reflow soldering should not be done more than two times.
4. Never take next process until the component is cooled down to room temperature after reflow.
5. The recommended reflow soldering profile (measuring on the surface of the LED terminal) is following:

### Lead-free Solder Profile



## Reworking

- Rework should be completed within 5 seconds under 260 °C.
- The iron tip must not come in contact with the copper foil.
- Twin-head type is preferred.

## Cleaning

Following are cleaning procedures after soldering:

- An alcohol-based solvent such as isopropyl alcohol (IPA) is recommended.
- Temperature x Time should be 50 °C x 30sec. or <30 °C x 3min
- Ultrasonic cleaning: < 15W/ bath; bath volume ≤ 1liter
- Curing: 100 °C max, <3min

Official Product	HT Part No. F10Q1FH--20P000742U1930			
Tentative Product	*****	*****		
Specifications are subject to changes for improvement without advance notice. Proprietary data, drawings, company confidential all rights reserved.		11/20/2024	Version 1.0	Page 15/16

**Cautions of Pick and Place**

- Avoid stress on the resin at elevated temperature.
- Avoid rubbing or scraping the resin by any object.
- Electric-static may cause damage to the component. Please ensure that the equipment is properly grounded. Use of an ionizer fan is recommended.

**Revision History**

Rev.	Descriptions	Date	Page
-	Preliminary	11/01/2024	-
1.0	Official Version	11/20/2024	-

Official Product	HT Part No. F10Q1FH--20P000742U1930		
Tentative Product	*****	*****	
Specifications are subject to changes for improvement without advance notice. Proprietary data, drawings, company confidential all rights reserved.	11/20/2024	Version 1.0	Page 16/16