

PRODUCT SPECIFICATION

Model No : CSST-FLDFCG4XX-A1X

Descriptions:CSST-FLDFCG4XX-A1X

- LED Type : SMD LED(Black Body)
: PLCC6 3.5x3.5x2.8mm
- Emitting Color : Full Color
- Encapsulation : Epoxy



CUSTOMER APPROVED SIGNATURES	APPROVED BY	CHECKED BY	PREPARED BY
	<div>2020.01.04</div> <div>YH</div> <div>All rights reserved</div>	<div>2020.01.04</div> <div>CYF</div> <div>All rights reserved</div>	<div>2020.01.04</div> <div>GY</div> <div>All rights reserved</div>

CS BRIGHT CORPORATION

Address : 11F, No.659, Ban-Nan Rd, Chung-Ho District, New Taipei City, Taiwan 235
Tel: 886-2-8221-1988
Fax: 886-2-8221-1336

<http://www.csbright.com>

OPTO PLUS TECHNOLOGIES CO.,LTD

Address : No.696, Yangming North Rd, ShaoXing City, ZheJiang Province, P.R.China
Tel : 86-575-88623888
Fax : 86-575-88623112



Model No.: CSST-FLDFCG4XX-A1X

■ Features –

1. PLCC-6 Package
2. High Luminous Output
3. Inside 3 chips
4. Wide viewing angle at 120 °
5. RoHS Compliant
6. Water-Resistant(IPX7)*
7. Compatible Lead-Free Reflow Soldering process

■ Applications –

1. Full-Color Video Screen
2. Decorative lighting
3. Amusement



Model No.: CSST-FLDFCG4XX-A1X

■ Absolute Maximum Ratings–

(Ta=25°C)

Parameter	Symbol	Rating		Unit
Power Dissipation	Pd	R	52	mW
		G	110	
		B	110	
Forward Current (DC)	IF	R	30	mA
		G	30	
		B	30	
Peak Forward Current *	IFP	R	100	mA
		G	100	
		B	100	
Reverse Voltage*	VR	5		V
ESD Sensitivity	ESD	1000		V
Operating Temp.	Topr	-40 ~ +100		℃
Storage Temp.	Tstg	-40 ~ +100		℃
Junction Temp. *	TJ	R	115	℃
		G	115	
		B	115	
Soldering Temperature	Tsol	Reflow Soldering: 260℃ for 10 sec. Hand Soldering: 350℃ for 3 sec.		

Notes:


1. Pulse width ≤ 0.1 msec, duty $\leq 1/10$
2. Proper current rating must be observed to maintain junction temperature below the maximum at all the time.
3. The device can not operated under continuous reverse voltage.



Model No.: CSST-FLDFCG4XX-A1X


Package Outline Dimensions and Polarity-

Unit: mm



Note: Tolerance of measurement of Dimension: $\pm 0.2\text{mm}$

Recommended Soldering Pad Pattern



2020.11.04
CS'Bright Corp.
All rights reserved.

Model No.: CSST-FLDFCG4XX-A1X

Electrical / Optical Characteristics – (Ta=25°C)

Parameter	Symbol		Min.	Typ.	Max.	Unit	Condition
Forward Voltage	V _F	R		2.0		V	I _F =20mA
		G		3.2			
		B		3.2			
Luminous Intensity	I _v	R		800		mcd	
		G		1600			
		B		440			
Peak Wavelength	λ _p	R		627		nm	
		G		514			
		B		462			
Dominant Wavelength	λ _d	R		622		nm	
		G		522			
		B		467			
Spectrum Radiation Bandwidth	Δ λ	R		18		nm	
		G		30			
		B		25			
Viewing Angle	2θ 1/2	R		120		deg	
		G		120			
		B		120			
Reverse Current	I _R	R			10	μA	V _R =5V
		G			10		
		B			10		
ESD Sensitivity	HBM				1000	V	MIL-STD-833G

Note: For each die



Model No.: CSST-FLDFCG4XX-A1X

■ **Luminous Intensity Rank Limits –**

Bin Code	Red		Unit
	Min	Max	
26	530	700	mcd
27	700	910	
28	910	1180	

Bin Code	Green		Unit
	Min	Max	
28	1050	1400	mcd
29	1400	1800	
30	1800	2340	

Bin Code	Blue		Unit
	Min	Max	
23	290	380	mcd
24	380	500	
25	500	650	

Note: Tolerance of measurement of Luminous Flux : $\pm 12\%$



Model No.: CSST-FLDFCG4XX-A1X

■ **Dominant Wavelength Rank Limits–**

Bin Code	Red		Unit
	Min	Max	
R1	614	619	nm
R2	619	624	
R3	624	629	

Bin Code	Green		Unit
	Min	Max	
TG1	517	522	nm
TG2	522	527	
TG3	527	532	

Bin Code	Blue		Unit
	Min	Max	
B6	461	466	nm
B7	466	471	
B8	471	476	

Note : Tolerance of measurement of Dominant Wavelength : ± 1 nm



Model No.: CSST-FLDFCG4XX-A1X

■ **Forward Voltage Rank Limits –**

Bin Code	Red		Unit
	Min	Max	
V1A	1.7	2.0	V
V1B	2.0	2.3	
V1C	2.3	2.6	

Bin Code	Green		Unit
	Min	Max	
V2A	2.4	2.7	V
V2B	2.7	3.0	
V2C	3.0	3.3	

Bin Code	Blue		Unit
	Min	Max	
V3A	2.6	2.9	V
V3B	2.9	3.2	
V3C	3.2	3.5	

Notice: Tolerance of measurement of Forward Voltage: $\pm 0.1V$



Model No.: CSST-FLDFCG4XX-A1X

■ **Typical Electrical / Optical Characteristics Curves –**
(Ta = 25°C Unless Otherwise Noted)

**Figure 1. Relative Luminous FLux
vs. Forward Current**





Figure2. Forward Current VS. Forward Voltage



2020.11.04
CS'Bright Corp.
All rights reserved

Model No.: CSST-FLDFCG4XX-A1X

Figuer3. Ambient Temperature VS Forward current






Figure 4. Relative Spectral Power Distribution vs. Wavelength



Model No.: CSST-FLDFCG4XX-A1X

Figure5. Relative Luminosity VS. Radiation Angle




2020.11.04
CS'Bright Corp.
All rights reserved

Model No.: CSST-FLDFCG4XX-A1X

Package –

1. Tape Dimension




Unit: mm

Symbol	A0	B0	K0	P0	P1	P2	T
Spec	3.60±0.1	3.60±0.1	3.10±0.1	4.00±0.1	8.00±0.1	2.00±0.1	0.3±0.05
Symbol	E	F	D0	D1	W		
Spec	1.75±0.1	5.50±0.1	1.50±0.1	2.3±0.1	12.0±0.1		



Model No.: CSST-FLDFCG4XX-A1X

2. Reel Dimension



Unit: mm


Notice: (1) Quantity: 2500PCS/Reel

(2) Tolerance unless mentioned is $\pm 0.2\text{mm}$



Model No.: CSST-FLDFCG4XX-A1X

3. Packing Model



■ Packing Amount

Package Name	Package Dimension		Distribution of the layer or box		Total Mount		Note
	Size	Unit	Amount	Unit	Amount	Unit	
Reel	330.2	mm	1	Reel	2500	Pcs	
Inner Box	405*385*95	mm	4	Reel	10000	Pcs	
Outer Box	395*395*410	mm	4	Inner Box	40000	Pcs	

Model No.: CSST-FLDFCG4XX-A1X


■ Soldering Characteristics

IR-reflow Condition (Pb free)

Area	Title	Symbol	Min	Max	Unit
(1)Preheat	Ramp-up rate	Vp	1	5	°C/sec
	temperature	Tp	150	–	°C
	time	tp	–	–	sec
(2)Equilibrium	Ramp-up rate	Ve	–	–	°C/sec
	temperature	Te	150	200	°C
	Time	te	60	120	sec
(3)Reflow	Ramp-up rate	Vr	1	5	°C/sec
	temperature	Tr	220	–	°C
	Time	tr	–	60	sec
	Peak temperature	Trp	–	260	°C
	Peak time	trp	–	10	sec
(4)Cooling	Ramp-down rate	Vc	3	6	°C/sec



Model No.: CSST-FLDFCG4XX-A1X



Hand Soldering (Iron Condition)

Soldering Iron:30W Max

Temperature 350°C Max (iron tip 260°C Max)

Soldering Time:3 Seconds Max(Once)



Model No.: CSST-FLDFCG4XX-A1X

■ **Reliability Test Program/ Reliability Test Item**

NO.	Test Item	Standard Test Method	Test Conditions	Test Duration	Failure Criteria	Units Failed/Tested
1	Resistance to Soldering Heat	JEITA ED-4701 300 301	Tsld=260°C, 10sec,reflows Pretreatment30°C,70%,168hrs		#1	0/20
2	Solderability (Reflow Soldering)	JEITA ED-4701 300 303A	Tsld=245±5°C,5sec. Lead-free Solder(Sn-3.0Ag-0.5Cu)		#3	0/20
3	Thermal Shock	JEITA ED-4701 300 307	-40°C~110°C 10min dwell, 10sec transfer,	100cycle s	#1	0/20
4	Temperature Cycle	JEITA ED-4701 100 105	-40°C (30min) ~25°C (5min) ~ 110°C (30min) ~25°C (5min)	100cycle s	#1	0/20
5	High Temperature Storage	JEITA ED-4701 200 201	Ta=110°C	1000hrs.	#1	0/20
6	Temperature Humidity	JEITA ED-4701 100 103	Ta=60°C, RH=90%	1000hrs.	#1	0/20
7	Low Temperature Storage	JEITA ED-4701 200 202	Ta=-40°C	1000hrs.	#1	0/20
8	Room Temperature		Ta=25°C, IF=20mA	1000 hrs.	#2	0/20
9	Low Temperature Operating life		Ta=-40°C, IF=20mA	1000hrs.	#2	0/20

Model No.: CSST-FLDFCG4XX-A1X

Failure Criteria

Criteria #	Items	Conditions	Failure Criteria
#1	Forward Voltage(VF)	IF=20mA	>U.S.L.X1.1
	Luminous Intensity(IV)	IF=20mA	<L.S.L.X0.7
#2	Forward Voltage(VF)	IF=20mA	>U.S.L.X1.1
	Luminous Intensity(IV)	IF=20mA	<L.S.L.X0.5
#3	Solderability		Less than 95% solder coverage

U.S.L.: Upper Specification limit L.S.L.: Lower Specification Limit



Model No.: CSST-FLDFCG4XX-A1X

■ Handling of Silicone Resin LEDs-

● Handling Indications

- i. When handling the product, do not touch it directly with bare hands as it may contaminate the surface and affect on optical characteristics. In the worst cases, excessive force to the product might result in catastrophic failure due to package damage and/or wire breakage.



- ii. When handling the product with tweezers, LEDs should only be handled from the side and make sure that excessive force is not applied to the resin portion of the product. Failure to comply can cause the resin portion of the product to be cut, chipped, delaminated and/or deformed, and wire to be broken, and thus resulting in catastrophic failure.




● Pick and place

Recommended conditions: Outer nozzle $> \Phi 2.4\text{mm}$

Avoid direct contact to the encapsulant with picking up nozzle. Failure to comply might result in pick and place processes or damage to encapsulant. In the worst cases, catastrophic failure of the LEDs due to wire deformation and/or breakage.



Model No.: CSST-FLDFCG4XX-A1X



■ Storage –

- Storage Conditions

- A. Before opening the package:

The LEDs should be kept at $\leq 40^{\circ}\text{C}$ and $\leq 90\%\text{RH}$. The LEDs should be used within a year. When storing the LEDs, moisture proof packaging with absorbent material (silica gel) is recommended.

- B. After opening the package:

The LEDs should be kept at $\leq 30^{\circ}\text{C}$ and $\leq 60\%\text{RH}$. The LEDs should be soldered within 672 hours (4 weeks) after opening the package. If unused LEDs remain, they should be stored in moisture proof packages, such as sealed containers with packages of moisture absorbent material (silica gel). It is also recommended to return the LEDs to the original moisture proof bag and to reseal the moisture proof bag again.

- If the moisture absorbent material (silica gel) has faded away or the LEDs have exceeded the storage time, baking treatment should be performed using the following conditions.

Baking treatment: more than 24 hours at $60 \pm 5^{\circ}\text{C}$

- This product has silver plated metal parts that are inside and/or outside the package body. The silver plating becomes tarnished when being exposed to an environment which contains corrosive gases. Any LED with tarnished leads may lead to poor solderability and deterioration of optical characteristics. Please do not expose the LEDs to corrosive atmosphere during storage.
- After assembly and during use, silver plating can be affected by the corrosive gases emitted by components and materials in close proximity of the LEDs within an end

Model No.: CSST-FLDFCG4XX-A1X

product, and the gases entering into the product from the external atmosphere. The above should be taken into consideration when designing.

■ Moisture Proof Package –

- When moisture is absorbed into the SMT package it may vaporize and expand during soldering. There is a possibility that this can cause exfoliation of the contacts and damage to the optical characteristics of the LEDs. For this reason, the moisture proof package is used to keep moisture to a minimum in the package.
- The moisture proof package is made of an aluminum moisture proof bag. A package of a moisture absorbent material (silica gel) is inserted into the aluminum moisture proof bag. The silica gel changes its color from blue to red as it absorbs moisture.
- Please avoid rapid transitions in ambient temperature, especially in high humidity environments where condensation can occur.

■ Recommended circuit –

- In designing a circuit, the current through each LED must not exceed the absolute maximum rating specified for each LED. It is recommended to use Circuit B which regulates the current flowing through each LED. In the meanwhile, when driving LEDs with a constant voltage in Circuit A, the current through the LEDs may vary due to the variation in forward voltage (VF) of the LEDs. In the worst case, some LED may be subjected to stresses in excess of the absolute maximum rating.



- This product should be operated in forward bias. A driving circuit must be designed so that the product is not subjected to either forward or reverse voltage while it is off. In particular, if a reverse voltage is continuously applied to the product; such operation can cause migration resulting in LED damage.

■ Heat Generation –

- Thermal design of the end product is of paramount importance. Please consider the

Model No.: CSST-FLDFCG4XX-A1X

heat generation of the LED when making the system design. The coefficient of temperature increase per input electric power is affected by the thermal resistance of the circuit board and density of LED placement on the board, as well as other components. It is necessary to avoid intense heat generation and operate within the maximum ratings given in this specification.

- The operating current should be decided after considering the ambient maximum temperature of LEDs.

■ Static Electricity –

- Static electricity or surge voltage damages the LEDs. It is recommended that a wrist band or an anti-electrostatic glove be used when handling the LEDs.
- All devices, equipment and machinery must be properly grounded. It is recommended that precautions be taken against surge voltage to the equipment that mounts the LEDs.
- When inspecting the final products in which LEDs were assembled, it is recommended to check whether the assembled LEDs are damaged by static electricity or not. It is easy to find static-damaged LEDs by a light-on test or a VF test at a lower current (below 1mA is recommended).
- Damaged LEDs will show some unusual characteristics such as the leak current remarkably increases, the forward voltage becomes lower, or the LEDs do not light at the low current.
- Criteria: (VF > 2.0V at IF=0.5mA)



■ Cleaning –

- It is recommended that isopropyl alcohol be used as a solvent for cleaning the LEDs. When using other solvents, it should be confirmed beforehand whether the solvents will dissolve the package and the resin or not. Freon solvents should not be used to clean the LEDs because of worldwide regulations.
- Do not clean the LEDs by the ultrasonic. When it is absolutely necessary, the influence of ultrasonic cleaning on the LEDs depends on factors such as ultrasonic power and the assembled condition. Before cleaning, a pre-test should be done to confirm whether any damage to the LEDs will occur.

Notice: The specifications are subject to change without notice. Please contact us for updated information

Model No.: CSST-FLDFCG4XX-A1X

■ **Change story**

REV.	Date	Change Description
A	2015.03.25	Original Version
B	2015.05.30	Change Packing Amount
C	2015.09.02	Change Appearance dimension
D	2016.1.07	Add Ink brush height
E	2016.1.23	Change Ambient Temperature VS Forward current
F	2016.04.19	Add ESD mark
G	2016.07.16	1、 Change Ambient Temperature VS Forward current 2、 Change Tape Dimension D1
H	2016.09.16	Change Packing Amount
J	2017.08.02	Change Reel Dimension
K	2019.03.21	1. Change Luminous Intensity Rank Limits 2. Change Electrical / Optical Characteristics 3. Change Dominant Wavelength Rank Limits
L	2020.01.04	1. Change Package Outline Dimensions and Polarity 2. Change Absolute Maximum Rating Polarity Notes

