

PROFET® Data Sheet BTS660P

Smart Highside High Current Power Switch

Reversave™

 Reverse battery protection by self turn on of power MOSFET

Features


- Overload protection
- Current limitation
- Short circuit protection
- Over temperature protection
- Over voltage protection (including load dump)
- Clamp of negative voltage at output
- Fast deenergizing of inductive loads ¹⁾
- Low ohmic inverse current operation
- Diagnostic feedback with load current sense
- Open load detection via current sense
- Loss of V_{bb} protection²⁾
- Electrostatic discharge (ESD) protection


Application


- Power switch with current sense diagnostic feedback for up to 48 V DC grounded loads
- Most suitable for loads with high inrush current like lamps and motors; all types of resistive and inductive loads
- Replaces electromechanical relays, fuses and discrete circuits


General Description

N channel vertical power FET with charge pump, current controlled input and diagnostic feedback with load current sense, integrated in Smart SIPMOS chip on chip technology. Providing embedded protective functions.









¹⁾ With additional external diode.

²⁾ Additional external diode required for energized inductive loads (see page 9).



Pin	Symbol		Function
1	OUT	0	Output to the load. The pins 1,2,6 and 7 must be shorted with each other especially in high current applications! 3)
2	OUT	0	Output to the load. The pins 1,2,6 and 7 must be shorted with each other especially in high current applications! 3)
3	IN	I	Input, activates the power switch in case of short to ground
4	Vbb	+	Positive power supply voltage, the tab is electrically connected to this pin. In high current applications the tab should be used for the V_{bb} connection instead of this pin ⁴).
5	IS	S	Diagnostic feedback providing a sense current proportional to the load current; zero current on failure (see Truth Table on page 7)
6	OUT	0	Output to the load. The pins 1,2,6 and 7 must be shorted with each other especially in high current applications! ³⁾
7	OUT	0	Output to the load. The pins 1,2,6 and 7 must be shorted with each other especially in high current applications! $^{3)}$

Maximum Ratings at $T_j = 25$ °C unless otherwise specified

Parameter	Symbol	Values	Unit
Supply voltage (over voltage protection see page 4)	$V_{ m bb}$	62	V
Supply voltage for full short circuit protection, (E _{AS} limitation see diagram on page 10) $T_{j,\text{start}}$ =-40+150°C:	$V_{ m bb}$	58	V
Load current (short circuit current, see page 5)	<i>I</i> L	self-limited	Α
Load dump protection $V_{\text{LoadDump}} = U_{\text{A}} + V_{\text{S}}$, $U_{\text{A}} = 13.5 \text{ V}$			
$R_1^{5} = 2 \Omega$, $R_L = 0.23 \Omega$, $t_d = 200 \text{ms}$,	V _{Load dump} ⁶)	80	V
IN, IS = open or grounded			
Operating temperature range	T _j	-40+150	°C
Storage temperature range	T_{stg}	-55+150	
Power dissipation (DC), T _C ≤ 25 °C	P _{tot}	170	W
Inductive load switch-off energy dissipation, single pulse $V_{bb} = 12V$, $T_{j,start} = 150$ °C, $T_{C} = 150$ °C const., $I_{L} = 20$ A, $Z_{L} = 6$ mH, 0Ω , see diagrams on page 10	E _{AS}	1.2	J
Electrostatic discharge capability (ESD) Human Body Model acc. MIL-STD883D, method 3015.7 and ESD assn. std. S5.1-1993, C = 100 pF, R = 1.5 k Ω	V _{ESD}	4.0	kV
Current through input pin (DC)	I _{IN}	+15, -250	mA
Current through current sense status pin (DC)	I _{IS}	+15, -250	
see internal circuit diagrams on page 7 and 8			

Not shorting all outputs will considerably increase the on-state resistance, reduce the peak current capability and decrease the current sense accuracy

Otherwise add up to 0.7 m Ω (depending on used length of the pin) to the R_{ON} if the pin is used instead of the tab.

 $R_{\rm I}$ = internal resistance of the load dump test pulse generator.

⁶⁾ V_{Load dump} is setup without the DUT connected to the generator per ISO 7637-1 and DIN 40839.



Thermal Characteristics

Parameter and Condit	Symbol	Values			Unit	
			min	typ	max	
Thermal resistance	chip - case:	R_{thJC^7}			0.75	K/W
j	R_{thJA}		60			
SME	O version, device on PCB 8):			33		

Electrical Characteristics

Parameter and Conditions	Symbol		Values	}	Unit
at $T_j = -40 \dots +150 ^{\circ}\text{C}$, $V_{bb} = 24 ^{\circ}\text{V}$ unless otherwise specified		min	typ	max	

Load Switching Capabilities and Characteristics

Load Switching Capabilities and Characteristics					
On-state resistance (Tab to pins 1,2,6,7, see					
measurement circuit page 7) $I_L = 20 \text{ A}, T_j = 25 \text{ °C}$:	Ron		7.2	9	$m\Omega$
$V_{IN} = 0$, $I_L = 20 \text{ A}$, $T_j = 150 \text{ °C}$:			14.6	17	
$I_{L} = 80 \text{ A}, T_{j} = 150 ^{\circ}\text{C}$:				17	
$V_{bb} = 6V$, $I_L = 20A$, $T_j = 150$ °C:	R _{ON(Static)}		17	22	
Nominal load current ⁹⁾ (Tab to pins 1,2,6,7)	I _{L(ISO)}	38	44	-	Α
ISO 10483-1/6.7: $V_{ON} = 0.5 \text{ V}$, $T_{C} = 85 ^{\circ}\text{C}^{-10}$					
Nominal load current 9), device on PCB 8)					
$T_A = 85 \text{ °C}, T_j \le 150 \text{ °C } V_{ON} \le 0.5 \text{ V},$	$I_{L(NOM)}$	9.9	11.1		A
Maximum load current in resistive range					
(Tab to pins 1,2,6,7) $V_{ON} = 1.8 \text{ V}, T_{C} = 25 ^{\circ}\text{C}$:	$I_{L(Max)}$	185			
see diagram on page 13 $V_{ON} = 1.8 \text{ V}, T_{C} = 150 ^{\circ}\text{C}$:		105			Α
Turn-on time ¹¹⁾ $I_{IN} \perp$ to 90% V_{OUT} :	<i>t</i> on	50		400	μs
Turn-off time $I_{IN} \perp$ to 10% V_{OUT} :	$t_{ m off}$	30		110	
$R_L = 1 \Omega$, $T_j = -40 + 150$ °C					
Slew rate on $^{11)}$ (10 to 30% V_{OUT})	d V/dt _{on}	1.0	1.5	2.2	V/μs
$R_{L} = 1 \Omega$					
Slew rate off $^{11)}$ (70 to 40% V_{OUT})	-d V/dt _{off}	1.1	1.9	2.6	V/μs
$R_{L} = 1 \Omega$					

Thermal resistance R_{thCH} case to heatsink (about 0.5 ... 0.9 K/W with silicone paste) not included!

Device on 50mm*50mm*1.5mm epoxy PCB FR4 with 6cm² (one layer, 70μm thick) copper area for V_{bb} connection. PCB is vertical without blown air.

⁹⁾ not subject to production test, specified by design

 $T_{\rm J}$ is about 105°C under these conditions.

¹¹⁾ See timing diagram on page 14.



 $I_{IN} = 0, V_{bb} = 35V$

Data Sheet BTS660P

25

50

Parameter and Conditions	Symbol		Unit			
at $T_j = -40 +150 ^{\circ}\text{C}$, $V_{bb} = 24 ^{\circ}\text{V}$ unless oth		min	typ	max		
Inverse Load Current Operation						
On-state resistance (Pins 1,2,6,7 to pin	ո 4)					
$V_{\text{bIN}} = 12 \text{ V}, I_{\text{L}} = -20 \text{ A}$	$T_j = 25 ^{\circ}\text{C}$:	$R_{ON(inv)}$		7.2	9	$m\Omega$
see diagram on page 10	$T_{\rm j} = 150 {\rm ^{\circ}C}$:			14.6	17	
Nominal inverse load current (Pins 1,	2,6,7 to Tab)	I _{L(inv)}	50	60		Α
$V_{ON} = -0.5 \text{V}, \ T_{C} = 85 ^{\circ}\text{C}$						
Drain-source diode voltage (Vout > Vb	-V _{ON}		0.6	0.7	mV	
$I_L = -20 \text{ A}, I_{IN} = 0, T_j = +150^{\circ}\text{C}$						
Operating Parameters						
Operating voltage (V _{IN} = 0) ¹²)		$V_{\rm bb(on)}$	5.0		58	V
Under voltage shutdown 13)14)		$V_{bIN(u)}$	1.5	3.0	4.5	V
Under voltage start of charge pump						
see diagram page 15		$V_{\text{bIN(ucp)}}$	3.0	4.5	6.0	V
Over voltage protection ¹⁵⁾	$T_{\rm j}$ =-40°C:	$V_{bIN(Z)}$	68			V
$I_{\rm bb} = 15\mathrm{mA}$ $T_{\rm j}$	=25+150°C:		70	72		
Standby current 7	T _j =-40+25°C:	I _{bb(off)}		15	25	μΑ

 $T_{\rm i} = 150^{\circ}{\rm C}$:

not subject to production test, specified by design

If the device is turned on before a V_{bb} -decrease, the operating voltage range is extended down to $V_{bIN(u)}$. For the voltage range 0..58 V the device is fully protected against overtemperature and short circuit.

 $V_{\text{bIN}} = V_{\text{bb}} - V_{\text{IN}}$ see diagram on page 15. When V_{bIN} increases from less than $V_{\text{bIN}(u)}$ up to $V_{\text{bIN}(ucp)} = 5 \text{ V}$ (typ.) the charge pump is not active and $V_{\text{OUT}} \approx V_{\text{bb}} - 3 \text{ V}$.

See also $V_{ON(CL)}$ in circuit diagram on page 9.



Parameter and Conditions	Symbol	Values			Unit
at $T_j = -40 \dots +150 ^{\circ}\text{C}$, $V_{bb} = 24 ^{\circ}\text{V}$ unless otherwise specified		min	typ	max	
Protection Functions ¹⁶⁾					
Short circuit current limit (Tab to pins 1,2,6,7)					
$V_{ON} = 24 \text{ V}$, time until shutdown max. $300 \mu\text{s}$ $T_{C} = -40 ^{\circ}\text{C}$:	I _{L(SC)}		90	180	Α
see page 8 and 13 $T_c = 25$ °C:	I _{L(SC)}		90		
$T_{\rm c}$ =+150°C:	I _{L(SC)}	50	80		
Short circuit shutdown delay after input current positive slope, $V_{\rm ON} > V_{\rm ON(SC)}^{17)}$ min. value valid only if input "off-signal" time exceeds 30 μ s	t _{d(SC)}	80		350	μs
Output clamp (inductive load switch off) at $V_{\text{OUT}} = V_{\text{bb}} - V_{\text{ON(CL)}}$ (e.g. over voltage) $I_{\text{L}} = 40 \text{ mA}$	V _{ON(CL)}	62	65	72	V
Short circuit shutdown detection voltage ¹⁷) (pin 4 to pins 1,2,6,7)	V _{ON(SC)}	1	6	!	V
Thermal overload trip temperature	$T_{\rm jt}$	150			°C
Thermal hysteresis	$\Delta T_{\rm jt}$		10		K

Reverse Battery

Reverse battery voltage 18)		- V _{bb}			42	V
On-state resistance (Pins 1,2,6,7 to pin 4)	$T_j = 25$ °C:	R _{ON(rev)}		8.8	10.5	$m\Omega$
V_{bb} =-12V, V_{IN} =0, I_{L} =-20A, R_{IS} =1k Ω	$T_{j} = 150 ^{\circ}\text{C}$:	, ,			20	
Integrated resistor in V _{bb} line	$T_{j} = 25 \mathrm{C}$:	R _{bb}	90	120	135	Ω
	<i>T</i> _j =150°C:		105	125	150	

¹⁶) Integrated protection functions are designed to prevent IC destruction under fault conditions described in the data sheet. Fault conditions are considered as "outside" normal operating range. Protection functions are not designed for continuous repetitive operation.

not subject to production test, specified by design

The reverse load current through the intrinsic drain-source diode has to be limited by the connected load (as it is done with all polarity symmetric loads). Note that under off-conditions ($I_{IN} = I_{IS} = 0$) the power transistor is not activated. This results in raised power dissipation due to the higher voltage drop across the intrinsic drain-source diode. The temperature protection is not active during reverse current operation! To reduce the power dissipation at the integrated R_{bb} resistor an input resistor is recommended as described on page 9.



Parameter and Conditions	Symbol		Values	3	Unit
at $T_j = -40 \dots +150 ^{\circ}\text{C}$, $V_{bb} = 24 ^{\circ}\text{V}$ unless otherwise specified		min	typ	max	

Diagnostic Characteristics

Current sense ratio, static on-condition, $I_L = 80 \text{ A}, T_j = -40^{\circ}\text{C}$: k_{ILIS} $I_{LIS} = I_L : I_{IS}$ I_{L)))
$V_{\text{bIN}} > 4.0 \text{V}$ $T_{\text{j}} = 150 ^{\circ}\text{C}$: see diagram on page 12 $I_{\text{L}} = 10 \text{A}$, $T_{\text{j}} = -40 ^{\circ}\text{C}$: $T_{\text{j}} = 25 ^{\circ}\text{C}$: $T_{\text{j}} = 25 ^{\circ}\text{C}$: $T_{\text{j}} = 25 ^{\circ}\text{C}$: $T_{\text{j}} = 150 ^{\circ}\text{C}$: $T_{\text{j}} = 150 ^{\circ}\text{C}$: $T_{\text{j}} = 150 ^{\circ}\text{C}$: $T_{\text{j}} = 25 ^{\circ}\text{C}$: $T_{\text{j}} = 150 ^{\circ}\text{C}$: T_{j	
Sense current saturation	mA
Current sense leakage current $I_{IN} = 0$ $I_{IS(LL)}$ 0.	+
	P
$V_{IN} = 0, I_{L} < 0: I_{IS(LH)}$ 2 6	
Current sense over voltage protection $T_j = -40^{\circ}\text{C}$: $V_{\text{blS}(Z)}$ 68	V
$I_{bb} = 15 \text{mA}$ $T_j = 25+150 ^{\circ}\text{C}$: 70 72	
Current sense settling time ²⁰)	μs

Input

Input and operating current (see diagram page 13) IN grounded (V _{IN} = 0)	I _{IN(on)}	 0.8	1.5	mA
Input current for turn-off ²¹)	I _{IN(off)}	 	80	μΑ

¹⁹⁾ If V_{ON} is higher, the sense current is no longer proportional to the load current due to sense current saturation, see $I_{IS,lim}$.

not subject to production test, specified by design

We recommend the resistance between IN and GND to be less than 0.5 k Ω for turn-on and more than 500k Ω for turn-off. Consider that when the device is switched off (I_{IN} = 0) the voltage between IN and GND reaches almost V_{bb}.



Truth Table

	Input current	Output	Current Sense	Remark
	level	level	lis	
Normal	L	L	0	
operation	Н	Н	nominal	=I _L / k _{ilis} , up to I _{IS} =I _{IS,lim}
Very high load current	Н	н	I _{IS, lim}	up to V _{ON} =V _{ON(Fold back)} I _{IS} no longer proportional to I _L
Current- limitation	н	Н	0	$V_{ON} > V_{ON(Fold back)}$ if $V_{ON} > V_{ON(SC)}$, shutdown will occure
Short circuit to	L	L	0	
GND	Н	L	0	
Over-	L	L	0	
temperature	Н	L	0	
Short circuit to	L	Н	0	
V_{bb}	Н	H	<nominal <sup="">22)</nominal>	
Open load	L	Z ²³)	0	
	Н	Н	0	
Negative output voltage clamp	L	L	0	
Inverse load	L	Н	0	
current	Н	Н	0	


L = "Low" Level

H = "High" Level

Over temperature reset by cooling: $T_{j} < T_{jt}$ (see diagram on page 15)


Short circuit to GND: Shutdown remains latched until next reset via input (see diagram on page 14)

Terms



Two or more devices can easily be connected in parallel to increase load current capability.

RON measurement layout




Typical RON for SMD version is about 0.2 m Ω less than straight leads due to I \approx 2 mm

Low ohmic short to V_{bb} may reduce the output current I_L and can thus be detected via the sense current I_{lS} .

Power Transistor "OFF", potential defined by external impedance.

Input circuit (ESD protection)




When the device is switched off ($I_{IN} = 0$) the voltage between IN and GND reaches almost V_{bb} . Use a bipolar or MOS transistor with appropriate breakdown voltage as driver.


 $V_{Z,IN} = 74 \text{ V (typ)}.$

Short circuit detection

Fault Condition: $V_{ON} > V_{ON(SC)}$ (6 V typ.) and t> $t_{d(SC)}$ (80 ...300 µs).



Current sense status output




 $V_{\rm Z,IS}$ = 74 V (typ.), $R_{\rm IS}$ = 1 k Ω nominal (or 1 k Ω /n, if n devices are connected in parallel). $I_{\rm S}$ = $I_{\rm L}/I_{\rm liis}$ can be driven only by the internal circuit as long as $V_{\rm out}$ - $V_{\rm IS}$ > 5 V. If you want measure load currents up to $I_{\rm L(M)}$, $R_{\rm IS}$

should be less than $\frac{V_{\text{bb}} - 5 \text{ V}}{I_{\text{L(M)}} / K_{\text{lils}}}$

Note: For large values of $R_{\rm IS}$ the voltage $V_{\rm IS}$ can reach almost $V_{\rm bb}$. See also over voltage protection. If you don't use the current sense output in your application, you can leave it open.


Inductive and over voltage output clamp



 V_{ON} is clamped to $V_{ON(Cl)} = 62 \text{ V}$ typ




Over voltage protection of logic part



 R_{bb} = 120 Ω typ., $V_{Z,IN}$ = $V_{Z,IS}$ = 74 V typ., R_{IS} = 1 k Ω nominal. Note that when over voltage exceeds 79 V typ. a voltage above 5V can occur between IS and GND, if R_V , $V_{Z,VIS}$ are not used.

Reverse battery protection



 $R_V \ge 1 \text{ k}\Omega$, $R_{\text{IS}} = 1 \text{ k}\Omega$ nominal. Add R_{IN} for reverse battery protection in applications with V_{bb} above $16V^{18}$;


recommended value: $\frac{1}{R_{\text{IN}}} + \frac{1}{R_{\text{IS}}} + \frac{1}{R_{\text{V}}} = \frac{0.1\text{A}}{|V_{\text{bb}}| - 12\text{V}}$ if D_S is not used (or $\frac{1}{R_{\text{IN}}} = \frac{0.1\text{A}}{|V_{\text{bb}}| - 12\text{V}}$ if D_S is used).

To minimize power dissipation at reverse battery operation, the overall current into the IN and IS pin should be about 120mA. The current can be provided by using a small signal diode D in parallel to the input switch, by using a MOSFET input switch or by proper adjusting the current through $R_{\rm IS}$ and $R_{\rm V}$.


V_{bb} disconnect with energized inductive load

Provide a current path with load current capability by using a diode, a Z-diode, or a varistor. (V_{ZL} < 70 V or V_{Zb} < 42 V if R_{IN}=0). For higher clamp voltages currents at IN and IS have to be limited to 250 mA.

Version a:




Version b:




Note that there is no reverse battery protection when using a diode without additional Z-diode V_{ZL} , V_{Zb} .

Version c: Sometimes a necessary voltage clamp is given by non inductive loads R_L connected to the same switch and eliminates the need of clamping circuit:






Inverse load current operation



The device is specified for inverse load current operation ($V_{\rm OUT} > V_{\rm bb} > 0V$). The current sense feature is not available during this kind of operation ($I_{\rm IS} = 0$). With $I_{\rm IN} = 0$ (e.g. input open) only the intrinsic drain source diode is conducting resulting in considerably increased power dissipation. If the device is switched on ($V_{\rm IN} = 0$), this power dissipation is decreased to the much lower value $R_{\rm ON(INV)} * P_{\rm IS} = 0$ (specifications see page 4).

Note: Temperature protection during inverse load current operation is not possible!

Inductive load switch-off energy dissipation



Energy stored in load inductance:

$$E_L = \frac{1}{2} \cdot L \cdot I_1^2$$

While demagnetizing load inductance, the energy dissipated in PROFET is


$$E_{AS} = E_{bb} + E_L - E_R = V_{ON(CL)} \cdot i_L(t) dt$$

with an approximate solution for $R_L > 0 \Omega$:

$$E_{AS} = \frac{I_L \cdot L}{2 \cdot R_L} (V_{bb} + |V_{OUT(CL)}|) ln (1 + \frac{I_L \cdot R_L}{|V_{OUT(CL)}|})$$

Maximum allowable load inductance for a single switch off

$$L = f(I_L)$$
; T_{j,start} = 150°C, V_{bb} = 40 V, R_L = 0 Ω




L [µH]

I [A]

Externally adjustable current limit

If the device is conducting, the sense current can be used to reduce the short circuit current and allow higher lead inductance (see diagram above). The device will be turned off, if the threshold voltage of T2 is reached by $\rm I_s^*R_{\rm ls}$. After a delay time defined by $\rm R_v^*C_v$ T1 will be reset. The device is turned on again, the short circuit current is defined by $\rm I_{L(SC)}$ and the device is shut down after $\rm t_{d(SC)}$ with latch function.





Options Overview

Type BTS	660P
Over temperature protection with hysteresis $T_i > 150 ^{\circ}\text{C}$, latch function ²⁴)	Х
$T_j > 150$ °C, with auto-restart on cooling	Х
Short circuit to GND protection switches off when $V_{\text{ON}}>6$ V typ. (when first turned on after approx. 180 μ s)	Х
Over voltage shutdown	-
Output negative voltage transient limit to V_{bb} - $V_{\text{ON(CL)}}$ to V_{OUT} = -15 V typ	X X ²⁵)

Latch except when $V_{\rm bb}$ - $V_{\rm OUT}$ < $V_{\rm ON(SC)}$ after shutdown. In most cases $V_{\rm OUT}$ = 0 V after shutdown ($V_{\rm OUT}$ \neq 0 V only if forced externally). So the device remains latched unless $V_{\rm bb}$ < $V_{\rm ON(SC)}$ (see page 5). No latch between turn on and $t_{\rm d(SC)}$.


²⁵⁾ Can be "switched off" by using a diode D_S (see page 8) or leaving open the current sense output.



Characteristics


Current sense versus load current:

 $I_{|S} = f(I_L), T_J = -40 \dots +150 \text{ °C}$ $I_{|S} \text{ [mA]}$



Current sense ratio:

 $K_{ILIS} = f(I_L), T_j = 25$ °C




/∟[A] kilis


/∟ [A]

Current sense ratio:

 $K_{ILIS} = f(I_L), T_j = -40$ °C k_{Ilis}



Current sense ratio: $K_{\text{ILIS}} = f(I_{\text{L}}), T_{\text{j}} = 150^{\circ}\text{C}$








Typ. current limitation characteristic

 $I_L = f(Von, T_j)$




In case of $V_{ON} > V_{ON(SC)}$ (typ. 6 V) the device will be switched off by internal short circuit detection.

Typ. on-state resistance

 $R_{ON} = f(V_{bb}, T_j); \ I_{L} = 20 \text{ A}; \ V_{IN} = 0$


RON [mOhm]



Typ. input current

 $I_{IN} = f(V_{bIN}), V_{bIN} = V_{bb} - V_{IN}$


IN [mA]






Timing diagrams

Figure 1a: Switching a resistive load, change of load current in on-condition:



The sense signal is not valid during a settling time after turn-on/off and after change of load current.

Figure 2b: Switching motors and lamps:



Sense current saturation can occur at very high inrush currents (see $I_{\text{IS,lim}}$ on page 6).

Figure 2c: Switching an inductive load:





Figure 3d: Short circuit: shut down by short circuit detection, reset by $I_{IN} = 0$.



Shut down remains latched until next reset via input.



Figure 4e: Overtemperature Reset if $T_j < T_{jt}$





Figure 6f: Undervoltage restart of charge pump, overvoltage clamp








Package and Ordering Code

All dimensions in mm


 TO-220-7-3
 Ordering code

 BTS660P
 Q67060-S6309




TO 220-7SMD, Opt. E3180 Ordering code

BTS660P E3180A T&R: Q67060-S6310



Footprint:



Published by Infineon Technologies AG, St.-Martin-Strasse 53, D-81669 München © Infineon Technologies AG 2001 All Rights Reserved.

Attention please!

The information herein is given to describe certain components and shall not be considered as a guarantee of characteristics.

Terms of delivery and rights to technical change reserved.

We hereby disclaim any and all warranties, including but not limited to warranties of non-infringement, regarding circuits, descriptions and charts stated herein.

Infineon Technologies is an approved CECC manufacturer.

Information

For further information on technology, delivery terms and conditions and prices please contact your nearest Infineon Technologies Office in Germany or our Infineon Technologies Representatives worldwide (see address list).

Warnings

Due to technical requirements components may contain dangerous substances. For information on the types in question please contact your nearest Infineon Technologies Office.

Infineon Technologies Components may only be used in lifesupport devices or systems with the express written approval of Infineon Technologies, if a failure of such components can reasonably be expected to cause the failure of that lifesupport device or system, or to affect the safety or effectiveness of that device or system. Life support devices or systems are intended to be implanted in the human body, or to support and/or maintain and sustain and/or protect human life. If they fail, it is reasonable to assume that the health of the user or other persons may be endangered.