

Automotive LPDDR5X SDRAM

MT62F512M32D1

Features

- **Architecture**
 - 19.2 GB/s maximum bandwidth per channel
 - Frequency range: 1200–5 MHz (data rate range per pin: 9600–40 Mb/s per-pin with WCK:CK = 4:1)
 - Selectable CKR (WCK:CK = 2:1 or 4:1)
- **LPDDR5/LPDDR5X data interface**
 - Dual x16 channel/die
 - Double-data-rate command/address entry
 - Differential command clocks (CK_t/CK_c) for high-speed operation
 - Differential data clocks (WCK_t/WCK_c)
 - Optional differential read strobe (RDQS_t/RDQS_c)
 - 16n-bit or 32n-bit prefetch architecture
 - Bank Architecture: Bank Group (BG) mode, and 16-bank (16B) mode supported
 - Command-selectable burst lengths (BL = 16 or 32) in bank group or 16-bank modes
 - Background ZQ cal/Cmd-based ZQ calibration
 - Optional link protection (link ECC)
 - Partial-array self refresh (PASR) and partial-array auto refresh (PAAR) with segment mask
- **Ultra-low-voltage core and I/O power supplies**
 - V_{DD1} = 1.70–1.95V; 1.80V TYP
 - V_{DD2H} = 1.01–1.12V; 1.05V TYP
 - V_{DD2L} = V_{DD2H} or 0.87–0.97V; 0.90V TYP
 - V_{DDQ} = 0.50V or 0.45V¹ TYP; 0.30V TYP (ODT off only)
- **I/O characteristics**
 - Interface-LVSTL 0.5/0.3
 - I/O type: Low-swing single-ended, V_{SS} terminated
 - V_{OH}-compensated output drive
 - Programmable V_{SS} on-die termination (ODT)
 - Non target ODT support
 - DVFSQ support
 - Per byte and per pin DFE support
- **Low power features**
 - Enhanced DVFSQ: Enhanced dynamic voltage frequency scaling core
 - Single-ended (CK, WCK, RDQS)
 - Data copy
 - Write X

Options

- **Operating Voltage**
 - V_{DD1}/V_{DD2H}/V_{DD2L}/V_{DDQ}/V_{DDQ} (ODT off only): 1.80V/1.05V/V_{DD2H} or 0.90V/0.50V or 0.45V¹/0.30V
- **Array Configuration**
 - 512Mb x 32 (512Mb x 16 x 1 Die x 2Ch x 1R) 512M32
- **Device configuration**
 - 1 die in package (512Mb32 x 1 die) D1
- **FBGA RoHS-compliant “green” package**
 - 315-ball TFBGA DS
 - 12.4mm x 15.0mm (TYP),
 - seated height 1.1mm (MAX)
- **Speed grade, cycle time (^tWCK)**
 - 9600 Mb/s per-pin -020
 - 8533 Mb/s per-pin -023
 - 7500 Mb/s per-pin -026
- **Functional Safety & DLEP**
 - Micron safety features enabled
 - Suitable for meeting random HW metrics up to ASIL D
 - Dynamic Link ECC Protocol (DLEP)
 - FMEDA (ISO 26262-5:2018, cl. 8, 9)
 - Safety manual F²
- **Automotive**
 - AEC-Q100 A
 - PPAP
 - ISO 26262 ASIL D compliant development
- **Operating temperature:**
 - -40°C ≤ T_C ≤ +95°C IT
 - -40°C ≤ T_C ≤ +105°C AT
 - -40°C ≤ T_C ≤ +125°C UT³
- **Revision**
 - :E

- Notes: 1. V_{DDQ} = 0.45V (TYP) support on all packages up to 7500 Mb/s per-pin.
2. For functional safety documentation to aid in ISO 26262 functional safety system design, contact Micron sales representative.
3. Based on automotive usage model. Contact Micron sales representative with questions.

Part Number Ordering Information

Figure 1: Part Number Chart




Table 1: Part Number List

Part Number	Total Density (package)	Data Rate per Pin
MT62F512M32D1DS-020 AAT:E	2GB (16Gb)	9600 Mb/s
MT62F512M32D1DS-020 AIT:E		
MT62F512M32D1DS-020 AUT:E		
MT62F512M32D1DS-020FAAT:E		
MT62F512M32D1DS-020FAIT:E		
MT62F512M32D1DS-020FAUT:E		
MT62F512M32D1DS-023 AIT:E		8533 Mb/s
MT62F512M32D1DS-023 AAT:E		
MT62F512M32D1DS-023 AUT:E		
MT62F512M32D1DS-023FAAT:E		
MT62F512M32D1DS-023FAIT:E		
MT62F512M32D1DS-023FAUT:E		

FBGA Part Marking Decoder

Due to space limitations, FBGA-packaged components have an abbreviated part marking that is different from the part number. Micron's FBGA part marking decoder is available at www.micron.com/decoder.

LPDDR5/LPDDR5X Data Sheet List

For general LPDDR5/LPDDR5X specifications, please refer to the data sheets below.

- General LPDDR5/LPDDR5X Specifications 1: Mode Registers
- General LPDDR5/LPDDR5X Specifications 2: AC/DC and Interface Specifications
- General LPDDR5/LPDDR5X Specifications 3: Features and Functionalities

Contents

Features.....	1
Part Number Ordering Information.....	2
FBGA Part Marking Decoder.....	2
LPDDR5/LPDDR5X Data Sheet List.....	2
Contents.....	3
List of Figures.....	4
List of Tables.....	5
Important Notes and Warnings.....	6
General Notes.....	7
Functional Safety Notes.....	8
Device Configuration.....	9
Refresh Requirement Parameters.....	11
CS Rx Relaxed Specification.....	12
DQ Rx Mask and Single Input Pulse Relaxed Specifications.....	12
DQ Rx Mask and Single Input Pulse Relaxed Specifications 3200 MHz.....	14
16-Bank Extended Frequency.....	15
16-Bank Extended Frequency Description.....	15
16B/BG Data Rate Change Diagram With FSP Requirements.....	16
Package Block Diagrams.....	17
Single Die, Dual Channel, Single Rank.....	17
Ball Assignments and Descriptions.....	18
315b Dual Channel, 1 Rank, 2 Rank.....	18
Package Dimensions.....	20
315-Ball Package (Package Code: DS).....	20
Package Thermal Impedance.....	21
Product-Specific Mode Register Definition.....	22
I _{DD} Parameters.....	25
Revision History.....	33
Rev. G – 05/2025.....	33
Rev. F – 02/2025.....	33
Rev. E – 01/2025.....	33
Rev. D – 11/2024.....	33
Rev. C – 09/2024.....	33
Rev. B – 05/2024.....	33
Rev. A – 01/2024.....	33

List of Figures

Figure 1: Part Number Chart..... 2

Figure 2: DQ Rx Mask Definition..... 13

Figure 3: LPDDR5X DQ Single Pulse Definition..... 14

Figure 4: 16B and BG Data Rate Change Flow Chart Showing Extended Capabilities..... 16

Figure 5: Single-Die, Dual-Channel, Single-Rank Package Block Diagram..... 17

Figure 6: 315-Ball Dual-Channel Discrete FBGA..... 19

Figure 7: 315-Ball TFBGA – 12.4mm (TYP) × 15.0mm (TYP) × 1.1mm (MAX) (Package Code: DS)..... 20

List of Tables

Table 1: Part Number List.....	2
Table 2: Die Organization in the Package (x32, 2Ch die).....	9
Table 3: Die Addressing per Channel.....	10
Table 4: Refresh Requirement Parameters.....	11
Table 5: CS Rx Specifications.....	12
Table 6: DQ Rx Mask and Single Input Pulse Specifications.....	12
Table 7: DQ, DMI, Parity and DBI Rx Mask and Single Input Pulse Specifications.....	14
Table 8: 16-Bank Operation ¹ @ 4.3 Gb/s.....	15
Table 9: 315-Ball/Pad Descriptions.....	18
Table 10: Package Thermal Impedance Characteristics.....	21
Table 11: Mode Register Contents.....	22
Table 12: I _{DD} Parameters at 7500 Mb/s – Single Channel of 2Ch Die.....	25
Table 13: I _{DD} Parameters at 8533 Mb/s – Single Channel of 2Ch Die.....	27
Table 14: I _{DD} Parameters at 9600 Mb/s – Single Channel of 2Ch Die.....	29
Table 15: I _{DD} Parameters at 3200 Mb/s – With Enhanced DVFSC Enabled - Single Channel of 2Ch Die.....	31
Table 16: Full-Array Power-Down Self Refresh Current – Single Channel of the 2 Ch Die.....	32

Important Notes and Warnings

Micron Technology, Inc. ("Micron") reserves the right to make changes to information published in this document, including without limitation specifications and product descriptions. This document supersedes and replaces all information supplied prior to the publication hereof. You may not rely on any information set forth in this document if you obtain the product described herein from any unauthorized distributor or other source not authorized by Micron.

Automotive Applications. Products are not designed or intended for use in automotive applications unless specifically designated by Micron as automotive-grade by their respective data sheets. Customer or distributor shall assume the sole risk and liability for and shall indemnify and hold Micron harmless against all claims, costs, damages, and expenses and reasonable attorneys' fees arising out of, directly or indirectly, any claim of product liability, personal injury, death, or property damage resulting directly or indirectly from any use of non-automotive-grade products in automotive applications. Customer/distributor shall ensure that the terms and conditions of sale between customer/distributor and any customer of customer/distributor (1) state that Micron products are not designed or intended for use in automotive applications unless specifically designated by Micron as automotive-grade by their respective data sheets and (2) require such customer of customer/distributor to indemnify and hold Micron harmless against all claims, costs, damages, and expenses and reasonable attorneys' fees arising out of, directly or indirectly, any claim of product liability, personal injury, death, or property damage resulting from any use of non-automotive-grade products in automotive applications.

System Design and Implementation. This product has been developed for multiple applications based on assumed use cases and requirements (including assumed functional safety requirements and constraints). It is the customer's sole responsibility to evaluate and confirm the validity and suitability of Micron's product datasheet, assumed use cases and requirements, and evaluation results by verifying Micron's assumptions against actual use cases and requirements in the intended end system and application. The customer must ensure compliance with all applicable requirements and standards (including industry, product, security, privacy, safety, etc.) to its system and applications. The customer must protect against death, personal injury, and severe property and environmental damage by ensuring that adequate design and redundancy (as needed), manufacturing and operating safeguards are included into customer's applications to ensure that failure of the Micron component will not result in such harms.

Customer Responsibility. Customers are responsible for the design, manufacture, and operation of their systems, applications, and products using Micron products. ALL SEMICONDUCTOR PRODUCTS HAVE INHERENT FAILURE RATES AND LIMITED USEFUL LIVES. IT IS THE CUSTOMER'S SOLE RESPONSIBILITY TO DETERMINE WHETHER THE MICRON PRODUCT IS SUITABLE AND FIT FOR THE CUSTOMER'S SYSTEM, APPLICATION, OR PRODUCT. Customers must ensure that adequate design, manufacturing, and operating safeguards are included in customer's applications and products to eliminate the risk that personal injury, death, or severe property or environmental damages will result from failure of any semiconductor component.

Limited Warranty. In no event shall Micron be liable for any indirect, incidental, punitive, special or consequential damages (including without limitation lost profits, lost savings, business interruption, costs related to the removal or replacement of any products or rework charges) whether or not such damages are based on tort, warranty, breach of contract or other legal theory, unless explicitly stated in a written agreement executed by Micron's duly authorized representative.

General Notes

Throughout the data sheet, figures and text refer to DQs as DQ. DQ should be interpreted as any or all DQs collectively, unless specifically stated otherwise.

RDQS, CK, and WCK should be interpreted as RDQS_t, RDQS_c, CK_t, CK_c, and WCK_t, WCK_c respectively unless specifically stated otherwise. CA includes all CA pins used for a given density.

In timing diagrams, CMD is used as an indicator only. Actual signals occur on CA[6:0].

V_{REF} indicates $V_{REF(CA)}$ and $V_{REF(DQ)}$.

Complete functionality is described throughout the entire document. Any page or diagram may have been simplified to convey a topic and may not be inclusive of all requirements.

Any content defined in this device ID specific data sheet document takes precedence over similar content defined in the general core LPDDR5/LPDDR5X SDRAM data sheet document(s).

Any functionality not specifically stated herein is considered undefined, illegal, is not supported, and will result in unknown operation.

Functional Safety Notes

This automotive LPDDR5/LPDDR5X DRAM product family has been developed according to ISO 26262:2018 requirements to provide a level of systematic fault coverage that allows its use in systems targeting up to ASIL D compliance.

This LPDDR5/LPDDR5X DRAM contains several new functional safety features that operate within the JEDEC LPDDR5/LPDDR5X protocols (commands, timings, and so forth) and are made available to the integrator on “F” parts (see Part Number Ordering Information). The specification addendum governing these functional safety features is available under NDA. This LPDDR5/LPDDR5X DRAM may operate as a standard JEDEC LPDDR5/LPDDR5X DRAM only, or as a standard JEDEC LPDDR5/LPDDR5X DRAM specifically designed to include functional safety features to communicate fault detection (only available on “F” parts). Additional support may be available to customers who need to integrate Micron’s products in their functional safety-related applications. This support may include Safety Analysis Report, reporting FMEDA results and metrics, Safety Manual and Pin FMEA Report, providing guidelines and instructions for using Micron products in safety-related applications.

Contact a Micron sales representative to initiate the process required to obtain the functional safety documentation.



Device Configuration

Table 2: Die Organization in the Package (x32, 2Ch die)

Die Organization	512M32 (16 Gb/package)
Channel A	x16 mode × 1Ch of 2Ch die
Channel B	x16 mode × 1Ch of 2Ch die

Note: 1. Refer to the Package Block Diagram section in this data sheet.

Table 3: Die Addressing per Channel

Description	512M32 (16 Gb/package) 2 Channel die	
Density per channel	8Gb	
Bits per channel	8,589,934,592	
Bank mode	BG mode	16B mode
Configuration	32Mb × 16 DQ × 4 Banks × 4BG	32Mb × 16 DQ × 16 Banks
Number of banks	4	16
Number of bank groups	4	1
Array prefetch bits	256	
Rows per bank	32,768	
Columns	64	
Page size (bytes)	2048	
Native burst length	16	
Number of I/Os	16	
Bank address	BA[1:0]	BA[3:0]
Bank group address	BG[1:0]	–
Row address	R[14:0]	
Column address	C[5:0]	
Burst address	B[3:0]	
Burst starting address boundary	128-bit	

Notes: 1. Refer to the SDRAM Addressing section in General LPDDR5/LPDDR5X Specifications 3.
2. Die addressing is aligned per channel in a 2 channel die

Refresh Requirement Parameters

Table 4: Refresh Requirement Parameters

Parameter	Symbol	8Gb Die	Unit
		BG and 16B Mode	
REFRESH cycle time (all banks)	t_{RFCab}	210	ns
REFRESH cycle time (per bank)	t_{RFCpb}	120	ns
Per bank refresh to per bank refresh time (different bank)	$t_{PBR2PBR}$	90	ns
Per bank refresh to ACTIVATE command time (different bank)	$t_{PBR2ACT}$	7.5	ns

Note: 1. This table only describes refresh parameters that are density dependent. Refer to Refresh Requirement section in General LPDDR5/LPDDR5X Specifications 3 for all refresh parameters.

CS Rx Relaxed Specification

Table 5: CS Rx Specifications

Item	Symbol	Min/ Max	CK Frequency (MHz)												Unit	Note
			67 ⁶	133	200	266	344	400	467	533	600	688	750	800		
Rx mask																
CS Rx mask height	vCSIVW	Min	155												mV	2, 7
CS Rx mask width at V _{REF} CS	^t CSIVW1	Min	0.3												UI	1
CS Rx mask width at vCSIVW	^t CSIVW2	Min	0.22												UI	1
Rx single pulse																
CS Rx pulse amplitude	vCSIHL_AC	Min	240												mV	3
CS reference voltage	vREFCS		V _{DD2H} /3												mV	
CS Rx pulse width	^t CSIPW	Min	0.6												UI	
Power down																
CS V _{IL} during power down/ deep sleep	V _{ILPD}	Max	130												mV	4
CS V _{IH} during power down/ deep sleep	V _{IHPD}	Min	550												mV	5
		Max	V _{DD2H} + 200													

- Notes: 1. CS Rx mask voltage and timing parameters at the pin include temperature drift and voltage AC noise impact based on Z(f) specification at a fixed temperature on the package. The voltage supply noise must comply to the component min/max DC operating conditions.
2. CS single-pulse signal amplitude into the receiver must meet or exceed vCSIHL_AC at any point over the total UI; No timing requirement above a certain level. vCSIHL_AC is the peak-to-peak voltage centered around V_{REF} CS such that vCSIHL_AC/2 min has to be met both above and below V_{REF} CS.
3. vCSIHL_AC does not have to be met when no transitions are occurring.
4. The input voltage presented to the CS Rx pin during power down should be 0V nominally to minimize leakage current.
5. V_{IHPD} is only applied for POWER DOWN and DEEP SLEEP EXIT operations.
6. The Rx voltage and absolute timing requirements apply for all CS operating frequencies at or below 67 for all speed bins. For example, ^tCSIVW1 (ns) = 4.477ns at or below 67 MHz CK frequency.
7. Measured at die pad.

DQ Rx Mask and Single Input Pulse Relaxed Specifications

Table 6: DQ Rx Mask and Single Input Pulse Specifications

Item	Symbol	Min/ Max	WCK Frequency (MHz)			Unit	Notes
			3750	4266	4800		
DQ Rx mask height	vDIVW	Min	70			mV	1, 2, 3
DQ Rx mask width at V _{REF} (DQ)	^t DIVW1	Min	0.35			UI	1, 3
DQ Rx mask width at vDIVW	^t DIVW2	Min	0.18			UI	1, 3
DQ Rx pulse width at V _{REF} (DQ)	^t DIPW1	Min	0.51			UI	4
DQ Rx pulse reference	^t DIPW2	Min	0.26			UI	4
DQ Rx pulse width at V _{REF} (DQ) ± vDIVW/2	^t DIHL	Min	0.24			UI	4
DQ Rx pulse amplitude from programmed V _{REF} (DQ)	vDIHP1	Min	70			mV	
	vDILP1	Max	-70			mV	

Table 6: DQ Rx Mask and Single Input Pulse Specifications (Continued)

Item	Symbol	Min/ Max	WCK Frequency (MHz)			Unit	Notes
			3750	4266	4800		
DQ Rx early pulse amplitude from programmed $V_{REF(DQ)}$	vDIHP2	Min	55			mV	
	vDILP2	Max	-55			mV	
DQ Vref	VrefDQ	Max	180			mV	
		Min	75			mV	
DQ to DQ Offset	tDQ2DQ	Max	30			ps	5

- Notes: 1. Data Rx mask voltage and timing parameters are applied per pin and include the DRAM DQ-to-DQS voltage AC noise impact for frequencies greater than TBD MHz and maximum voltage of TBD mV peak-to-peak from DC-TBD MHz at a fixed temperature on the package. The voltage supply noise must comply with the component min/max DC operating conditions.
2. Rx mask voltage vDIVW must be centered around $V_{REF(DQ)}$.
3. Mask specifications (t_{DIVW1} , t_{DIVW2} , and vDIVW) are the same regardless DFE enabled or disabled. DFE co-efficient can be included as part of input waveform amplitude when DFE is enabled.
4. UI = $t_{WCK}/2$, programed V_{REF} , is defined as a percentage of MR14/15 code x V_{DDQ} .
5. DQ to DQ offset defined within byte from DRAM pin to internal latch for a given component.

Figure 2: DQ Rx Mask Definition





Figure 3: LPDDR5X DQ Single Pulse Definition



Note: 1. $vDIHL_AC/2 = vDIHP1 = vDILP1$. Programmed $V_{REF(DQ)}$ is defined as percentage of MR14/15 code * V_{DDQ} .

DQ Rx Mask and Single Input Pulse Relaxed Specifications 3200 MHz

Table 7: DQ, DMI, Parity and DBI Rx Mask and Single Input Pulse Specifications

Item	Symbol	Min/Max	WCK Frequency (MHz)	Unit	Notes
			3200		
DQ Rx mask height	vDIVW	Min	70	mV	1, 2, 3, 6
DQ Rx mask width at $V_{REF(DQ)}$	t_{DIVW1}	Min	0.35	UI	1, 3
DQ Rx mask width at vDIVW	t_{DIVW2}	Min	0.18	UI	1, 3
DQ Rx pulse width at $V_{REF(DQ)}$	t_{DIPW1}	Min	0.51	UI	4, 6
DQ Rx pulse reference	t_{DIPW2}	Min	0.26	UI	4
DQ Rx pulse width at $V_{REF(DQ)} \pm vDIVW/2$	t_{DIHL}	Min	0.24	UI	4, 6
DQ Rx pulse amplitude from programmed $V_{REF(DQ)}$	vDIHP1	Min	70	mV	
	vDILP1	Max	-70	mV	
DQ Rx early pulse amplitude from programmed $V_{REF(DQ)}$	vDIHP2	Min	55	mV	
	vDILP2	Max	-55	mV	
DQ V_{REF}	$V_{REF(DQ)}$	Min	75	mV	6
		Max	180	mV	6
DQ to DQ offset	t_{DQ2DQ}	Max	30	ps	5

Notes: 1. Data Rx mask voltage and timing parameters are applied per pin and include the DRAM DQ-to-DQS voltage AC noise impact for frequencies greater than TBD MHz and maximum voltage of TBD mV peak-to-peak from DC-TBD MHz at a fixed temperature on the package. The voltage supply noise must comply with the component min/max DC operating conditions.

2. Rx mask voltage vDIVW must be centered around $V_{REF(DQ)}$.

3. Mask specifications (t_{DIVW1} , t_{DIVW2} , and vDIVW) are the same regardless DFE enabled or disabled. DFE coefficient can be included as part of input waveform amplitude when DFE is enabled.

4. UI = $t_{WCK}/2$, programed V_{REF} , is defined as a percentage of MR14/15 code x V_{DDQ} .

5. DQ to DQ offset defined within byte from DRAM pin to DRAM internal latch for a given component.
6. When vDIVV is 70mV or more and less than 80mV.

16-Bank Extended Frequency

16-Bank Extended Frequency Description

Micron's LPDDR5 SDRAM device which are marked with 8533 Mb/s per-pin (-023) capability can support frequency set points using 2:1 WCK to CK ratio and above the 1600 MHz limit. Shown in the table below is specification requirements when considering 1867 MHz and 2133 MHz frequencies. This support is not available on 1-alpha process node and earlier Device ID's, this feature can expand capabilities of your system.

Table 8: 16-Bank Operation¹ @ 4.3 Gb/s

Parameter	3733 Mb/s per-pin	Comments	4267 Mb/s per-pin	Comments
RL Set 1/2/3	20/22/24	MR2[3:0] = 1100	23/25/26	MR2[3:0] = 1101
nRBTP	6		6	
WL Set A/B	11/19	MR1[7:4] = 1100	12/22	MR1[7:4] = 1101
nWR x16/x8	32/34	MR2[7:4] = 1100	37/39	MR2[7:4] = 1101
^t WCKPRE_static ²	5	Follows 7500 data rate	6	Follows 8533 data rate
^t WCKPRE_WR_toggle	4	Follows 3200 data rate	4	Follows 3200 data rate
^t WCKPRE_RD_toggle	10	Follows 3200 data rate	10	Follows 3200 data rate
^t WCKENL_FS	2	Follows 3200 data rate	2	Follows 3200 data rate
^t WCKPRE_toggle_FS ³	14	Minimum	16	Minimum
ODTLon	WL - 4	Follows 3200 data rate	WL - 4	Follows 3200 data rate
ODTLoff ⁴	WL + 5 (BL16), WL + 9 (BL32)	Follows 3200	WL + 5 (BL16), WL + 9 (BL32)	Follows 3200 data rate
ODTLoff_RD_DQ	RL - 4	Follows 3200 data rate	RL - 4	Follows 3200 data rate
ODTLoff_RD_RDQS	RL - 6	MR10 OP[1, 5:4] = 000, 001, 010	RL - 6	MR10 OP[1, 5:4] = 000, 001, 010
	RL - 8	MR10 OP[1, 5:4] = 011, 1XX	RL - 8	MR10 OP[1, 5:4] = 011, 1XX
ODTLon_RD_DQ ⁵	RL + 6 (BL16), RL + 10 (BL32)		RL + 6 (BL16), RL + 10 (BL32)	
ODTLon_RD_RDQS ⁶	RL + 8 (BL16), RL + 12 (BL32)		RL + 8 (BL16), RL + 12 (BL32)	

Notes: 1. Restricted to WCK:CK 2:1 ratio, WCK:CK 4:1 ratio not supported; Link ECC is disabled, and DVFSC/E-DVFSC is disabled.

2. Common for WR/RD/FS.

3. Minimum 1 + RL - (^tWCKENL_FS + ^tWCKPRE_Static) when CAS to RD is 1CK.


4. (WL + BL/n_min + RU(^tWCK2DQI(max)/^tCK)).

5. (RL + BL/n_min + RU(^tWCK2DQO(max)/^tCK)).

6. (RL + BL/n_min + RU(^tWCK2DQO(max)/^tCK)) + 2.

7. 8533 MT/s or higher data rated parts support 16-bank mode up to 4267 MT/s with restrictions, all other speed rated parts greater than 3200 MT/s per-pin and less than 8533 MT/s per-pin are restricted from the extended 16B


8. When operating in the 16-bank mode, the FSP procedure must be used when setting the data rate above 3.2 Gb/s per-pin even when setting for the first time. For example, if the device is powered-up and initialized for 4266 Gb/s per-pin timing at the initial operation start, the FSP procedure must still be used. See Figure 4: 16B and BG Data Rate Change Flow Chart Showing Extended Capabilities on page 16 for details of FSP usage.



Package Block Diagrams

Single Die, Dual Channel, Single Rank

Figure 5: Single-Die, Dual-Channel, Single-Rank Package Block Diagram



Ball Assignments and Descriptions

315b Dual Channel, 1 Rank, 2 Rank

Table 9: 315-Ball/Pad Descriptions

Symbol	Type	Description
CK_t_[A:B], CK_c_[A:B]	Input	Clock: CK_t and CK_c are differential clock inputs. All double data rate (DDR) command/address inputs are sampled on both crossing points of CK_t and CK_c. The first crossing point is the rising (falling) edge of CK_t (CK_c) and second crossing point is falling (rising) edge of CK_t (CK_c). Single data rate (SDR) inputs, CS is sampled on the crossing point that is the rising (falling) edge of CK_t (CK_c).
CS0_[A:B], CS1_[A:B]	Input	Chip select: CS is part of the command code, and is sampled on the rising (falling) edge of CK_t (CK_c) unless the device is in power-down or deep sleep mode where it becomes an asynchronous signal. Each rank (0, 1) has its own CS signals. CS1_[A:B] become NC pins in a single-rank package.
CA[6:0]_[A:B]	Input	Command/address inputs: Provide the command and address inputs according to the command truth table.
WCK[1:0]_t_[A:B], WCK[1:0]_c_[A:B]	Input	Data clock: WCK_t and WCK_c are differential clock inputs used for write data capture and read data output.
DQ[15:0]_[A:B]	I/O	Data input/output: Bidirectional data bus.
RDQS[1:0]_t_[A:B], RDQS[1:0]_c_[A:B]	I/O Output	Read data strobe: RDQS_t and RDQS_c are differential output clock signals used to strobe data during a READ operation. RDQS_t is also used as a parity pin during write link protection enabled. Each byte of data has RDQS_t and RDQS_c signals.
DMI[1:0]_[A:B]	I/O	Data mask inversion: DMI serves multiple functions such as data mask (DM), data bus inversion (DBI), and parity at READ with ECC operation by setting the mode register. DMI is a bidirectional signal and each byte of data has a DMI signal.
ZQ_A	Reference	ZQ calibration reference: Used to calibrate the output drive strength and the termination resistance. The ZQ pin should be connected to V _{DDQ} through a 240 ohm $\pm 1\%$ resistor.
V _{DDQ} , V _{DD1} , V _{DD2H} , V _{DD2L}	Supply	Power supplies: Isolated on the die for improved noise immunity.
V _{SS}	Supply	Ground reference: Power supply ground reference.
RESET_n	Input	Reset: When asserted LOW, the RESET pin resets the die. Reset is an asynchronous signal.
NC	–	No connect: Not internally connected.
RFU	–	Reserved Future Use: Not internally connected.

Figure 6: 315-Ball Dual-Channel Discrete FBGA

	1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	
A	NC	NC	V _{DDQ}	DMI0_A	V _{SS}	V _{DD2L}	V _{DD2H}	V _{DD2H}	V _{DD2H}	V _{DD2L}	V _{SS}	DMI1_A	V _{DDQ}	NC	NC	A
B	NC	V _{DDQ}	RDQS0_t_A	V _{SS}	DQ4_A	V _{DD2L}	V _{DD2H}	V _{SS}	V _{DD2H}	V _{DD2L}	DQ12_A	V _{SS}	RDQS1_t_A	V _{DDQ}	NC	B
C	V _{DD1}	DQ1_A	V _{DDQ}	RDQS0_c_A	V _{SS}	DQ5_A	V _{DD2H}	V _{SS}	V _{DD2H}	DQ13_A	V _{SS}	RDQS1_c_A	V _{DDQ}	DQ9_A	V _{DD1}	C
D	DQ0_A	V _{SS}	DQ3_A	V _{DDQ}	WCK0_c_A	V _{SS}	V _{SS}	V _{DD2H}	V _{SS}	V _{SS}	WCK1_c_A	V _{DDQ}	DQ11_A	V _{SS}	DQ8_A	D
E	V _{SS}	DQ2_A	V _{SS}	WCK0_t_A	V _{DDQ}	DQ6_A	V _{DD2H}	V _{SS}	V _{DD2H}	DQ14_A	V _{DDQ}	WCK1_t_A	V _{SS}	DQ10_A	V _{SS}	E
F	V _{DDQ}	V _{SS}	V _{DDQ}	V _{DDQ}	DQ7_A	V _{DD2H}	V _{DD2H}	V _{SS}	V _{DD2H}	V _{DD2H}	DQ15_A	V _{DDQ}	V _{DDQ}	V _{SS}	V _{DDQ}	F
G	V _{DDQ}	V _{DDQ}	V _{SS}	CA0_A	V _{SS}	CS1_A	V _{SS}	CA2_A	V _{SS}	CA4_A	V _{SS}	CA6_A	V _{SS}	V _{DDQ}	V _{DDQ}	G
H	RESET_N	V _{DD2L}	V _{SS}	V _{SS}	CA1_A	V _{SS}	CS0_A	V _{SS}	CK_t_A	V _{SS}	CA3_A	V _{SS}	CA5_A	V _{DD2L}	ZQ_A	H
J	V _{SS}	V _{DD2L}	V _{SS}	RFU	V _{DD2H}	RFU	V _{SS}	V _{SS}	CK_c_A	V _{SS}	V _{DD2H}	V _{SS}	V _{SS}	V _{DD2L}	V _{SS}	J
K	V _{DD2H}	V _{DD2H}	V _{DD2H}	V _{DD2H}	V _{DD2H}	V _{DD2H}	V _{SS}	V _{SS}	V _{SS}	V _{DD2H}	V _{DD2H}	V _{DD2H}	V _{DD2H}	V _{DD2H}	V _{DD2H}	K
L	V _{SS}	V _{SS}	V _{SS}	V _{SS}	V _{SS}	V _{DD2H}	V _{DD2H}	V _{DD2H}	V _{DD2H}	V _{DD2H}	V _{SS}	V _{SS}	V _{SS}	V _{SS}	V _{SS}	L
M	V _{DD2H}	V _{DD2H}	V _{DD2H}	V _{DD2H}	V _{DD2H}	V _{DD2H}	V _{SS}	V _{SS}	V _{SS}	V _{DD2H}	V _{DD2H}	V _{DD2H}	V _{DD2H}	V _{DD2H}	V _{DD2H}	M
N	V _{SS}	V _{DD2L}	V _{SS}	V _{SS}	V _{DD2H}	V _{SS}	CK_c_B	V _{SS}	V _{SS}	V _{SS}	V _{DD2H}	V _{SS}	V _{SS}	V _{DD2L}	V _{SS}	N
P	RFU	V _{DD2L}	CA5_B	V _{SS}	CA3_B	V _{SS}	CK_t_B	V _{SS}	CS0_B	V _{SS}	CA1_B	V _{SS}	V _{SS}	V _{DD2L}	RFU	P
R	V _{DDQ}	V _{DDQ}	V _{SS}	CA6_B	V _{SS}	CA4_B	V _{SS}	CA2_B	V _{SS}	CS1_B	V _{SS}	CA0_B	V _{SS}	V _{DDQ}	V _{DDQ}	R
T	V _{DDQ}	V _{SS}	V _{DDQ}	V _{DDQ}	DQ15_B	V _{DD2H}	V _{DD2H}	V _{SS}	V _{DD2H}	V _{DD2H}	DQ7_B	V _{DDQ}	V _{DDQ}	V _{SS}	V _{DDQ}	T
U	V _{SS}	DQ10_B	V _{SS}	WCK1_t_B	V _{DDQ}	DQ14_B	V _{DD2H}	V _{SS}	V _{DD2H}	DQ6_B	V _{DDQ}	WCK0_t_B	V _{SS}	DQ2_B	V _{SS}	U
V	DQ8_B	V _{SS}	DQ11_B	V _{DDQ}	WCK1_c_B	V _{SS}	V _{SS}	V _{DD2H}	V _{SS}	V _{SS}	WCK0_c_B	V _{DDQ}	DQ3_B	V _{SS}	DQ0_B	V
W	V _{DD1}	DQ9_B	V _{DDQ}	RDQS1_c_B	V _{SS}	DQ13_B	V _{DD2H}	V _{SS}	V _{DD2H}	DQ5_B	V _{SS}	RDQS0_c_B	V _{DDQ}	DQ1_B	V _{DD1}	W
Y	NC	V _{DDQ}	RDQS1_t_B	V _{SS}	DQ12_B	V _{DD2L}	V _{DD2H}	V _{SS}	V _{DD2H}	V _{DD2L}	DQ4_B	V _{SS}	RDQS0_t_B	V _{DDQ}	NC	Y
AA	NC	NC	V _{DDQ}	DMI1_B	V _{SS}	V _{DD2L}	V _{DD2H}	V _{DD2H}	V _{DD2H}	V _{DD2L}	V _{SS}	DMI0_B	V _{DDQ}	NC	NC	AA
	1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	


Top View (ball down)

VSS
V_{DD1}
V_{DD2H}
V_{DD2L}
V_{DDQ}
CK
RDQS
WCK
DQ,DMI
CA, CS, ZQ, RESET
NC, RFU

Package Dimensions

315-Ball Package (Package Code: DS)

Figure 7: 315-Ball TFBGA – 12.4mm (TYP) × 15.0mm (TYP) × 1.1mm (MAX) (Package Code: DS)



Notes: 1. All dimensions are in millimeters.

2. Solder ball composition: SACQ with CuOSP pads (Sn-4Ag-0.5Cu-3Bi-0.05Ni)

Package Thermal Impedance

Table 10: Package Thermal Impedance Characteristics

Die Revision	Package	Parameter	Symbol	Value	Unit
Rev E	315-ball, SDP, package code DS	Junction-to-case (TOP)	Θ_{JC}	5.2	°C/W
		Junction-to-board	Θ_{JB}	11.2	°C/W

Note: 1. Thermal impedance values provided are for reference only. These values are based on a model and represent a maximum characteristic.

Product-Specific Mode Register Definition

Table 11: Mode Register Contents

Mode Register	OP7	OP6	OP5	OP4	OP3	OP2	OP1	OP0
MR0	Per-pin DFE	Pre Emphasis	Unified NT ODT behavior mode	DMI output behavior mode	Optimized refresh mode	Enhanced WCK always-on mode	Latency mode	NT ODT timing mode
	OP[0] = 1b: Device supports different NT ODT latency for DQ and RDQS							
	OP[1] = 0b: Device supports x16 mode latency for 512M32							
	OP[2] = 1b: Device supports enhanced WCK always-on mode							
	OP[3] = 1b: Device supports optimized refresh mode							
	OP[4] = 1b: Device supports both DMI behavior mode 1 and 2 and mode selection							
	OP[5] = 1b: The NT ODT behavior follows the unified NT ODT behavior							
	OP[6] = 1b: Device supports Pre Emphasis mode							
	OP[7] = 1b: Device supports Per Pin DFE							
MR1						DRFM support ³	ARFM support ³	CS ODT OP support
	OP[0] = 1b: Device supports CS ODT behavior OP							
	OP[1] = 1b: Device supports ARFM							
	OP[2] = 0b: Device does not support DRFM							
MR3				BK/BG ORG				
	OP[4:3] = 00b: BG mode supported							
	01b: 8B mode not supported							
	10b: 16B Mode supported							
	11b: RFU							
MR4				Refresh Multiplier (Note 7, 8)				
	OP[4:0]: Refer to General LPDDR5/LPDDR5X Specification 1 for mode register definitions.							
MR5	Manufacturer ID							
	1111 1111b: Micron							
MR6	Revision ID1							
	0001 1000b							
MR8	I/O width		Density				Device Type ⁶	
	OP[7:6] = 00b: x16 for 512M32		OP[5:2] = 0100b: 8Gb				OP[1:0] = 01b: LPDDR5X SDRAM (up to 8533 Mb/s) OP[1:0] = 10b: LPDDR5X SDRAM (up to 9600 Mb/s)	
MR13						VRO		
	OP[2] = 0b: Normal operation (default) 1b: Output the V _{REF(CA)} value on DQ7 and V _{REF(DQ)} value on DQ6							

Table 11: Mode Register Contents (Continued)

Mode Register	OP7	OP6	OP5	OP4	OP3	OP2	OP1	OP0								
MR19			WCK2DQ OSC FM													
	OP[5] = 1b: WCK2DQ OSC FM supported															
MR21	WXS				ODTD-CSFS	WXFS	RDCFS	WDCFS								
		OP[0] = 1b: WRITE DATA COPY function supported														
		OP[1] = 1b: READ DATA COPY function supported														
		OP[2] = 1b: WRITE X function supported														
		OP[3] = 1b: Device ODTD-CS is supported														
		OP[7] = 1b: Data to be written can be selected with 0 and 1														
		MR22	RECC	WECC												
OP[5:4] = 00b: Write link ECC disabled (default) 01b: Write link ECC enabled (See Note 4)																
OP[7:6] = 00b: Read link ECC disabled (default) 01b: Read link ECC enabled (See Note 4)																
MR24	DFES				Read DCA											
		OP[3] = 1b: Device supports Read DCA														
		OP[7] = 1b: Device supports DFE (See Note 5)														
MR26		RDQSTFS														
	OP[6] = 1b: Read/write-based RDQS_t TRAINING function supported															
MR27	RAAMULT		RAAIMT					RFM								
									OP[0] = 1b: RFM is required							
									OP[5:1] = 00110b: 48							
									OP[7:6] = 01b: 4X							
MR41					E-DVFSC ODT	DVFSC/ E-DVFSC Support										
	OP[2:1] = 10b: Both DVFSC and Enhanced DVFSC Mode supported															
	OP[3] = 1b: Enhanced DVFSC ODT option is supported															
MR43		SBEC rule														
	OP[6] = 1b: Simultaneous SBE on each DQ byte and DMI are independently counted															
MR57	ARFM ³		RFMSB		RFMSB		RAADEC									
									OP[1:0] = 10b: 2 × RAAIMT							
									OP[3:2] = 00b: Single Bank Mode not supported							
									OP[5:4] = 00b: One RAA counter per two banks (1 of 8)							
									OP[7:6] = 00b: default (00110b: 48), 01b: Level A, 10b: Level B, 11b: Level C							

- Notes: 1. The contents of mode registers described here reflect information specific to each die in these packages.
2. Refer to General LPDDR5/LPDDR5X Specification 1 for mode registers not described here.
3. Refer to General LPDDR5/LPDDR5X Specification 3 for feature description not described here.
4. Write link ECC and read link ECC are supported.
5. Device supports 7-step DFE.
6. Device type only supports Bank Group and 16B modes.

7. MR4:OP[4:0] output from each die in a defined package shall be used to determine the required package level refresh rate. Any other method used to determine a valid refresh rate, places ownership and responsibility of the correct refresh rate on the system developer or end user. TOPER (case surface temperature) shall be used to determine whether operating temperature requirements are being met. Any other method used to determine operating temperature, places ownership and responsibility of the correct operating temperature on the system developer or end user.
8. The intent of a MR4 OP[4:0] output of <01111> is to not to support a refresh rate of 0.125xd; rather a method to inform the host the die temperature is most likely being operated beyond its supported upper maximum limit and the host should immediately place the DRAM in to a refresh only state at 0.125xd refresh rate until the MR4 readout of <01111> no longer exists. No other operation other than refresh should be conducted.

I_{DD} Parameters

Refer to I_{DD} Specification Parameters and Test Conditions section in General LPDDR5/LPDDR5X Specifications 2 for detailed conditions. Data rate in IDD tables is defined as per-pin.

Table 12: I_{DD} Parameters at 7500 Mb/s – Single Channel of 2Ch Die

Symbol	Supply	Speed per-pin			Unit	Note
		x16 Mode				
		UT	AT	IT		
I _{DD01}	V _{DD1}	4.2	3.8	3.8	mA	
I _{DD02H}	V _{DD2H}	79	57	57		
I _{DD02L}	V _{DD2L}	0.2	0.2	0.2		
I _{DD0Q}	V _{DDQ}	0.6	0.6	0.6		
I _{DD2P1}	V _{DD1}	2.1	1.7	1.7	mA	
I _{DD2P2H}	V _{DD2H}	7.4	4.2	4.2		
I _{DD2P2L}	V _{DD2L}	0.2	0.2	0.2		
I _{DD2PQ}	V _{DDQ}	0.6	0.6	0.6		
I _{DD2PS1}	V _{DD1}	2.1	1.7	1.7	mA	
I _{DD2PS2H}	V _{DD2H}	7.4	4.2	4.2		
I _{DD2PS2L}	V _{DD2L}	0.2	0.2	0.2		
I _{DD2PSQ}	V _{DDQ}	0.6	0.6	0.6		
I _{DD2N1}	V _{DD1}	2	1.5	1.5	mA	
I _{DD2N2H}	V _{DD2H}	58	39	39		
I _{DD2N2L}	V _{DD2L}	0.2	0.2	0.2		
I _{DD2NQ}	V _{DDQ}	0.6	0.6	0.6		
I _{DD2NS1}	V _{DD1}	2	1.5	1.5	mA	
I _{DD2NS2H}	V _{DD2H}	58	39	39		
I _{DD2NS2L}	V _{DD2L}	0.2	0.2	0.2		
I _{DD2NSQ}	V _{DDQ}	0.6	0.6	0.6		
I _{DD3P1}	V _{DD1}	3.4	2.9	2.9	mA	
I _{DD3P2H}	V _{DD2H}	25	16	16		
I _{DD3P2L}	V _{DD2L}	0.2	0.2	0.2		
I _{DD3PQ}	V _{DDQ}	0.6	0.6	0.6		
I _{DD3PS1}	V _{DD1}	3.4	2.9	2.9	mA	
I _{DD3PS2H}	V _{DD2H}	25	16	16		
I _{DD3PS2L}	V _{DD2L}	0.2	0.2	0.2		
I _{DD3PSQ}	V _{DDQ}	0.6	0.6	0.6		
I _{DD3N1}	V _{DD1}	3.5	3	3	mA	
I _{DD3N2H}	V _{DD2H}	70	48	48		
I _{DD3N2L}	V _{DD2L}	0.2	0.2	0.2		
I _{DD3NQ}	V _{DDQ}	0.6	0.6	0.6		

Table 12: I_{DD} Parameters at 7500 Mb/s – Single Channel of 2Ch Die (Continued)

Symbol	Supply	Speed per-pin			Unit	Note
		x16 Mode				
		UT	AT	IT		
I _{DD4R1}	V _{DD1}	15	14	14	mA	3, 4, 6
I _{DD4R2H}	V _{DD2H}	440	387	387		
I _{DD4R2L}	V _{DD2L}	0.2	0.2	0.2		
I _{DD4RQ}	V _{DDQ}	111	111	111		
I _{DD4W1}	V _{DD1}	13	13	13	mA	3, 6
I _{DD4W2H}	V _{DD2H}	332	287	287		
I _{DD4W2L}	V _{DD2L}	0.2	0	0		
I _{DD4WQ}	V _{DDQ}	0.6	0.6	0.6		
I _{DD51}	V _{DD1}	16	15	15	mA	
I _{DD52H}	V _{DD2H}	186	149	149		
I _{DD52L}	V _{DD2L}	0.2	0.2	0.2		
I _{DD5Q}	V _{DDQ}	0.6	0.6	0.6		
I _{DD5AB1}	V _{DD1}	3.9	3.5	3.5	mA	
I _{DD5AB2H}	V _{DD2H}	68	48	48		
I _{DD5AB2L}	V _{DD2L}	0.2	0.2	0.2		
I _{DD5ABQ}	V _{DDQ}	0.6	0.6	0.6		
I _{DD5PB1}	V _{DD1}	3.9	3.5	3.5	mA	
I _{DD5PB2H}	V _{DD2H}	68	48	48		
I _{DD5PB2L}	V _{DD2L}	0.2	0.2	0.2		
I _{DD5PBQ}	V _{DDQ}	0.6	0.6	0.6		

- Notes: 1. Published I_{DD} values except I_{DD4RQ} are the maximum I_{DD} values considering the worst-case conditions of process, temperature, and voltage.
2. BG mode enabled. Enhanced DVFSC and DVFSQ disabled.
3. BL = 16, DBI disabled.
4. I_{DD4RQ} value is reference only. Typical value. Output load = 5pF; R_{ON} = 40 ohms; T_C = 25°C
5. V_{DD1} = 1.70–1.95V; V_{DD2H} = 1.01–1.12V; V_{DD2L} = 0.87–0.97V; V_{DDQ} = 0.47–0.57V (DVFSQ disabled)/0.27–0.37V (DVFSQ enabled)
6. IDD4R2 and IDD4W2 have implemented a more stringent pattern than required by JEDEC and therefore these IDD values are slightly higher than if the JEDEC pattern was used.
7. Notes 1, 2, and 5 apply to entire table.

Table 13: I_{DD} Parameters at 8533 Mb/s – Single Channel of 2Ch Die

Symbol	Supply	Speed per-pin			Unit	Note
		x16 Mode				
		UT	AT	IT		
I _{DD01}	V _{DD1}	4.2	3.8	3.8	mA	
I _{DD02H}	V _{DD2H}	79	57	57		
I _{DD02L}	V _{DD2L}	0.2	0.2	0.2		
I _{DD0Q}	V _{DDQ}	0.6	0.6	0.6		
I _{DD2P1}	V _{DD1}	2.1	1.7	1.7	mA	
I _{DD2P2H}	V _{DD2H}	7.4	4.2	4.2		
I _{DD2P2L}	V _{DD2L}	0.2	0.2	0.2		
I _{DD2PQ}	V _{DDQ}	0.6	0.6	0.6		
I _{DD2PS1}	V _{DD1}	2.1	1.7	1.7	mA	
I _{DD2PS2H}	V _{DD2H}	7.4	4.2	4.2		
I _{DD2PS2L}	V _{DD2L}	0.2	0.2	0.2		
I _{DD2PSQ}	V _{DDQ}	0.6	0.6	0.6		
I _{DD2N1}	V _{DD1}	2	1.5	1.5	mA	
I _{DD2N2H}	V _{DD2H}	58	39	39		
I _{DD2N2L}	V _{DD2L}	0.2	0.2	0.2		
I _{DD2NQ}	V _{DDQ}	0.6	0.6	0.6		
I _{DD2NS1}	V _{DD1}	2	1.5	1.5	mA	
I _{DD2NS2H}	V _{DD2H}	58	39	39		
I _{DD2NS2L}	V _{DD2L}	0.2	0.2	0.2		
I _{DD2NSQ}	V _{DDQ}	0.6	0.6	0.6		
I _{DD3P1}	V _{DD1}	3.4	2.9	2.9	mA	
I _{DD3P2H}	V _{DD2H}	25	16	16		
I _{DD3P2L}	V _{DD2L}	0.2	0.2	0.2		
I _{DD3PQ}	V _{DDQ}	0.6	0.6	0.6		
I _{DD3PS1}	V _{DD1}	3.4	2.9	2.9	mA	
I _{DD3PS2H}	V _{DD2H}	25	16	16		
I _{DD3PS2L}	V _{DD2L}	0.2	0.2	0.2		
I _{DD3PSQ}	V _{DDQ}	0.6	0.6	0.6		
I _{DD3N1}	V _{DD1}	3.5	3	3	mA	
I _{DD3N2H}	V _{DD2H}	70	48	48		
I _{DD3N2L}	V _{DD2L}	0.2	0.2	0.2		
I _{DD3NQ}	V _{DDQ}	0.6	0.6	0.6		
I _{DD4R1}	V _{DD1}	17	16	16	mA	3, 4, 6
I _{DD4R2H}	V _{DD2H}	474	421	421		
I _{DD4R2L}	V _{DD2L}	0.2	0.2	0.2		
I _{DD4RQ}	V _{DDQ}	121	121	121		

Table 13: I_{DD} Parameters at 8533 Mb/s – Single Channel of 2Ch Die (Continued)

Symbol	Supply	Speed per-pin			Unit	Note
		x16 Mode				
		UT	AT	IT		
I _{DD4W1}	V _{DD1}	15	15	15	mA	3, 6
I _{DD4W2H}	V _{DD2H}	359	313	313		
I _{DD4W2L}	V _{DD2L}	0.2	0	0		
I _{DD4WQ}	V _{DDQ}	0.6	0.6	0.6		
I _{DD51}	V _{DD1}	16	15	15	mA	
I _{DD52H}	V _{DD2H}	186	149	149		
I _{DD52L}	V _{DD2L}	0.2	0.2	0.2		
I _{DD5Q}	V _{DDQ}	0.6	0.6	0.6		
I _{DD5AB1}	V _{DD1}	3.9	3.5	3.5	mA	
I _{DD5AB2H}	V _{DD2H}	68	48	48		
I _{DD5AB2L}	V _{DD2L}	0.2	0.2	0.2		
I _{DD5ABQ}	V _{DDQ}	0.6	0.6	0.6		
I _{DD5PB1}	V _{DD1}	3.9	3.5	3.5	mA	
I _{DD5PB2H}	V _{DD2H}	68	48	48		
I _{DD5PB2L}	V _{DD2L}	0.2	0.2	0.2		
I _{DD5PBQ}	V _{DDQ}	0.6	0.6	0.6		

- Notes: 1. Published I_{DD} values except I_{DD4RQ} are the maximum I_{DD} values considering the worst-case conditions of process, temperature, and voltage.
2. BG mode enabled. Enhanced DVFSC and DVFSQ disabled.
3. BL = 16, DBI disabled.
4. I_{DD4RQ} value is reference only. Typical value. Output load = 5pF; R_{ON} = 40 ohms; T_C = 25°C
5. V_{DD1} = 1.70–1.95V; V_{DD2H} = 1.01–1.12V; V_{DD2L} = 0.87–0.97V; V_{DDQ} = 0.47–0.57V (DVFSQ disabled)/0.27–0.37V (DVFSQ enabled)
6. IDD4R2 and IDD4W2 have implemented a more stringent pattern than required by JEDEC and therefore these IDD values are slightly higher than if the JEDEC pattern was used.
7. Notes 1, 2, and 5 apply to entire table.

Table 14: I_{DD} Parameters at 9600 Mb/s – Single Channel of 2Ch Die

Symbol	Supply	Speed per-pin			Unit	Note
		x16 Mode				
		UT	AT	IT		
I _{DD01}	V _{DD1}	4.2	3.8	3.8	mA	
I _{DD02H}	V _{DD2H}	79	57	57		
I _{DD02L}	V _{DD2L}	0.2	0.2	0.2		
I _{DD0Q}	V _{DDQ}	0.6	0.6	0.6		
I _{DD2P1}	V _{DD1}	2.1	1.7	1.7	mA	
I _{DD2P2H}	V _{DD2H}	7.4	4.2	4.2		
I _{DD2P2L}	V _{DD2L}	0.2	0.2	0.2		
I _{DD2PQ}	V _{DDQ}	0.6	0.6	0.6		
I _{DD2PS1}	V _{DD1}	2.1	1.7	1.7	mA	
I _{DD2PS2H}	V _{DD2H}	7.4	4.2	4.2		
I _{DD2PS2L}	V _{DD2L}	0.2	0.2	0.2		
I _{DD2PSQ}	V _{DDQ}	0.6	0.6	0.6		
I _{DD2N1}	V _{DD1}	2	1.5	1.5	mA	
I _{DD2N2H}	V _{DD2H}	58	39	39		
I _{DD2N2L}	V _{DD2L}	0.2	0.2	0.2		
I _{DD2NQ}	V _{DDQ}	0.6	0.6	0.6		
I _{DD2NS1}	V _{DD1}	2	1.5	1.5	mA	
I _{DD2NS2H}	V _{DD2H}	58	39	39		
I _{DD2NS2L}	V _{DD2L}	0.2	0.2	0.2		
I _{DD2NSQ}	V _{DDQ}	0.6	0.6	0.6		
I _{DD3P1}	V _{DD1}	3.4	2.9	2.9	mA	
I _{DD3P2H}	V _{DD2H}	25	16	16		
I _{DD3P2L}	V _{DD2L}	0.2	0.2	0.2		
I _{DD3PQ}	V _{DDQ}	0.6	0.6	0.6		
I _{DD3PS1}	V _{DD1}	3.4	2.9	2.9	mA	
I _{DD3PS2H}	V _{DD2H}	25	16	16		
I _{DD3PS2L}	V _{DD2L}	0.2	0.2	0.2		
I _{DD3PSQ}	V _{DDQ}	0.6	0.6	0.6		
I _{DD3N1}	V _{DD1}	3.5	3	3	mA	
I _{DD3N2H}	V _{DD2H}	70	48	48		
I _{DD3N2L}	V _{DD2L}	0.2	0.2	0.2		
I _{DD3NQ}	V _{DDQ}	0.6	0.6	0.6		
I _{DD4R1}	V _{DD1}	18.5	17.5	17.5	mA	3, 4, 6
I _{DD4R2H}	V _{DD2H}	509	455	455		
I _{DD4R2L}	V _{DD2L}	0.2	0.2	0.2		
I _{DD4RQ}	V _{DDQ}	121.5	121.5	121.5		

Table 14: I_{DD} Parameters at 9600 Mb/s – Single Channel of 2Ch Die (Continued)

Symbol	Supply	Speed per-pin			Unit	Note
		x16 Mode				
		UT	AT	IT		
I _{DD4W1}	V _{DD1}	16.5	16	16	mA	3, 6
I _{DD4W2H}	V _{DD2H}	386	340	340		
I _{DD4W2L}	V _{DD2L}	0.2	0	0		
I _{DD4WQ}	V _{DDQ}	0.6	0.6	0.6		
I _{DD51}	V _{DD1}	16	15	15	mA	
I _{DD52H}	V _{DD2H}	186	149	149		
I _{DD52L}	V _{DD2L}	0.2	0.2	0.2		
I _{DD5Q}	V _{DDQ}	0.6	0.6	0.6		
I _{DD5AB1}	V _{DD1}	3.9	3.5	3.5	mA	
I _{DD5AB2H}	V _{DD2H}	68	48	48		
I _{DD5AB2L}	V _{DD2L}	0.2	0.2	0.2		
I _{DD5ABQ}	V _{DDQ}	0.6	0.6	0.6		
I _{DD5PB1}	V _{DD1}	3.9	3.5	3.5	mA	
I _{DD5PB2H}	V _{DD2H}	68	48	48		
I _{DD5PB2L}	V _{DD2L}	0.2	0.2	0.2		
I _{DD5PBQ}	V _{DDQ}	0.6	0.6	0.6		

- Notes: 1. Published I_{DD} values except I_{DD4RQ} are the maximum I_{DD} values considering the worst-case conditions of process, temperature, and voltage.
2. BG mode enabled. Enhanced DVFSQ and DVFSQ disabled.
3. BL = 16, DBI disabled.
4. I_{DD4RQ} value is reference only. Typical value. Output load = 5pF; R_{ON} = 40 ohms; T_C = 25°C
5. V_{DD1} = 1.70–1.95V; V_{DD2H} = 1.01–1.12V; V_{DD2L} = 0.87–0.97V; V_{DDQ} = 0.47–0.57V (DVFSQ disabled)/0.27–0.37V (DVFSQ enabled)
6. IDD4R2 and IDD4W2 have implemented a more stringent pattern than required by JEDEC and therefore these IDD values are slightly higher than if the JEDEC pattern was used.
7. Notes 1, 2, and 5 apply to entire table.

Table 15: I_{DD} Parameters at 3200 Mb/s – With Enhanced DVFS Enabled - Single Channel of 2Ch Die

Symbol	Supply	Speed per-pin			Unit	Note
		x16 Mode				
		UT	AT	IT		
I _{DD4R-DVFS} C1	V _{DD1}	9	8	8	mA	3, 4, 6
I _{DD4R-DVFS} C2H	V _{DD2H}	42	32	32		
I _{DD4R-DVFS} C2L	V _{DD2L}	123	105	105		
I _{DD4R-DVFS} CQ	V _{DDQ}	76	76	76		
I _{DD4W-DVFS} C1	V _{DD1}	8	8	8	mA	3, 6
I _{DD4W-DVFS} C2H	V _{DD2H}	39	29	29		
I _{DD4W-DVFS} C2L	V _{DD2L}	105	87	87		
I _{DD4W-DVFS} CQ	V _{DDQ}	0.6	0.6	0.6		
I _{DD5ED} 1	V _{DD1}	14	14	14	mA	
I _{DD5ED} 2H	V _{DD2H}	129	110	110		
I _{DD5ED} 2L	V _{DD2L}	35	23	23		
I _{DD5ED} Q	V _{DDQ}	0.6	0.6	0.6		
I _{DD5ABED} 1	V _{DD1}	3.7	3.3	3.3	mA	
I _{DD5ABED} 2H	V _{DD2H}	30	22	22		
I _{DD5ABED} 2L	V _{DD2L}	30	22	22		
I _{DD5ABED} Q	V _{DDQ}	0.6	0.6	0.6		
I _{DD5PBED} 1	V _{DD1}	3.7	3.3	3.3	mA	
I _{DD5PBED} 2H	V _{DD2H}	30	22	22		
I _{DD5PBED} 2L	V _{DD2L}	30	22	22		
I _{DD5PBED} Q	V _{DDQ}	0.6	0.6	0.6		

- Notes: 1. Published I_{DD} values except I_{DD4RQ} are the maximum I_{DD} values considering the worst-case conditions of process, temperature, and voltage.
2. Enhanced DVFS enabled, DVFSQ enabled, 3200 Mb/s, 16B mode
3. BL = 16, DBI disabled.
4. I_{DD4RQ} value is reference only. Typical value. Output load = 5pF; R_{ON} = 40 ohms; T_C = 25°C
5. V_{DD1} = 1.70–1.95V; V_{DD2H} = 1.01–1.12V; V_{DD2L} = 0.87–0.97V; V_{DDQ} = 0.47–0.57V (DVFSQ disabled)/0.27–0.37V (DVFSQ enabled)
6. IDD4R2 and IDD4W2 have implemented a more stringent pattern than required by JEDEC and therefore these IDD values are slightly higher than if the JEDEC pattern was used.
7. Notes 1, 2, and 5 apply to entire table.

Table 16: Full-Array Power-Down Self Refresh Current – Single Channel of the 2 Ch Die

Temperature	Symbol	Supply	Value	Unit	Notes
25°C	I _{DD61}	V _{DD1}	0.17	mA	
	I _{DD62H}	V _{DD2H}	0.42		
	I _{DD62L}	V _{DD2L}	0.01	mA	4
	I _{DD6Q}	V _{DDQ}	0.03		
	I _{DD6DS1}	V _{DD1}	0.17	mA	
	I _{DD6DS2H}	V _{DD2H}	0.42		
	I _{DD6DS2L}	V _{DD2L}	0.01	mA	4
	I _{DD6DSQ}	V _{DDQ}	0.03		
45°C	I _{DD61}	V _{DD1}	0.23	mA	
	I _{DD62H}	V _{DD2H}	0.75		
	I _{DD62L}	V _{DD2L}	0.01	mA	4
	I _{DD6Q}	V _{DDQ}	0.03		
	I _{DD6DS1}	V _{DD1}	0.23	mA	
	I _{DD6DS2H}	V _{DD2H}	0.75		
	I _{DD6DS2L}	V _{DD2L}	0.01	mA	4
	I _{DD6DSQ}	V _{DDQ}	0.03		
65°C	I _{DD61}	V _{DD1}	0.4	mA	
	I _{DD62H}	V _{DD2H}	2.0		
	I _{DD62L}	V _{DD2L}	0.01	mA	4
	I _{DD6Q}	V _{DDQ}	0.03		
	I _{DD6DS1}	V _{DD1}	0.4	mA	
	I _{DD6DS2H}	V _{DD2H}	2.0		
	I _{DD6DS2L}	V _{DD2L}	0.01	mA	4
	I _{DD6DSQ}	V _{DDQ}	0.03		
85°C	I _{DD61}	V _{DD1}	1.2	mA	
	I _{DD62H}	V _{DD2H}	7.0		
	I _{DD62L}	V _{DD2L}	0.2	mA	4
	I _{DD6Q}	V _{DDQ}	0.6		
	I _{DD6DS1}	V _{DD1}	1.2	mA	
	I _{DD6DS2H}	V _{DD2H}	7.0		
	I _{DD6DS2L}	V _{DD2L}	0.2	mA	4
	I _{DD6DSQ}	V _{DDQ}	0.6		

- Notes: 1. I_{DD625/45/65°C} is the typical value in the distribution with nominal V_{DD} and a reference-only value. I_{DD685°C} is the maximum I_{DD} guaranteed value considering the worst-case conditions of process, temperature, and voltage.
2. DVFSC and DVFSQ disabled.
3. V_{DD1} = 1.70–1.95V; V_{DD2H} = 1.01–1.12V; V_{DD2L} = 0.87–0.97V; V_{DDQ} = 0.47–0.57V
4. While entering and exiting Self-Refresh modes, all defined/used supply rails (V_{DD1}, V_{DD2H}, V_{DD2L}, V_{DDQ}) are required to be at valid levels. After the Self-Refresh with Power down mode entrance commands are completed and t_{ESPD} timing requirement has been satisfied, the V_{DDQ} power rail may be turned off by the controller.

Revision History

Rev. G – 05/2025

- Updated Features page
- Updated Part Number Ordering Information page
- Updated Important Notes and Warnings page
- Added Automotive Product Notes Page
- Updated Functional Safety, DLEP & RAS Notes page
- Updated Mode Register settings
- Production data sheet release

Rev. F – 02/2025

- Updated all IDD tables

Rev. E – 01/2025

- Updated the 9600Mbps IDD current values.

Rev. D – 11/2024

- Added "F" MPNs

Rev. C – 09/2024

- Added RxMask adjusted spec for 9600Mbps data rate.
- Added all 7500Mbps and 8533Mbps IDD values with associated notes to the datasheet
- Disabled DRFM support
- Added "F" part numbers

Rev. B – 05/2024

- Preliminary data sheet release

Rev. A – 01/2024

- Initial advanced data sheet release

8000 S. Federal Way, P.O. Box 6, Boise, ID 83707-0006
 208-368-4000, micron.com/support

Micron and the Micron logo are trademarks of Micron Technology, Inc.
 All other trademarks are the property of their respective owners.

This data sheet contains minimum and maximum limits specified over the power supply and temperature range set forth herein.
 Although considered final, these specifications are subject to change, as further product development and data characterization sometimes occur.