

Superior high Flux for High Voltage System

### High-Power LED - 5050 Series

### S1W0-5050xx06-00000000-00001





## **Product Brief**

#### Description

- This White Colored surface-mount LED comes in standard package dimension. Package Size : 5.0x5.0x0.7mm
- It has a substrate made up of a molded plastic reflector sitting on top of a lead frame.
- The die is attached within the reflector cavity and the cavity is encapsulated by silicone.
- The package design coupled with careful selection of component materials allow these products to perform with high reliability

#### **Features and Benefits**

- High Intensity output and high luminance
- Designed for high voltage operation
- SMT solderable
- RoHS compliant

#### **Key Applications**

- General lighting
- Architectural lighting
- LED Bulbs
- Decorative / Pathway lighting

Reference Code	Color	Nominal	Part Number	CRI
	00101	ССТ		Min
		6500K	S1W0-5050657006-0000000-00001	
	Cool White	5700K	5700K S1W0-5050577006-0000000-00001	
		5000K	S1W0-5050507006-0000000-00001	
STW0L6PA	Neutral White Warm White	4500K	S1W0-5050457006-00000000-00001	70
STWULOPA		4000K	S1W0-5050407006-00000000-00001	- 70
-		3500K	S1W0-5050357006-00000000-00001	
		3000K	S1W0-5050307006-00000000-00001	-
		2700K	S1W0-5050277006-00000000-00001	-

#### Table 1. Product Selection Table





SEOUL

S1W0-5050xx06-0000000-00001 -5050 Series

# **Table of Contents**

Inde	ex a constant of the second	
•	Product Brief	1
•	Table of Contents	2
•	Performance Characteristics	3
•	Characteristics Graph	5
•	Color Bin Structure	13
•	Mechanical Dimensions	17
•	Recommended Solder Pad	18
•	Reflow Soldering Characteristics	19
•	Emitter Tape & Reel Packaging	20
•	Product Nomenclature	22
•	Handling of Silicone Resin for LEDs	23
•	Precaution For Use	24
•	Company Information	27



## **Product Performance & Characterization Guide**

Min. CRI, Ra <sup>[4]</sup>	Nominal CCT [K] <sup>[1]</sup>	Min. Flux [lm]	Typ. Luminous Flux Φ <sub>v</sub> <sup>[2,3]</sup> [lm] @750mA	Typ. Luminous Efficacy [Im/W] @750mA	Part Number
	6500	670	725	151	S1W0-5050657006-00000000-00001
	5700	670	730	151	S1W0-5050577006-00000000-00001
	5000	720	740	153	S1W0-5050507006-00000000-00001
70	4500	720	740	153	S1W0-5050457006-00000000-00001
10	4000	720	740	153	S1W0-5050407006-00000000-00001
	3500	670	718	149	S1W0-5050357006-00000000-00001
	3000	670	715	148	S1W0-5050307006-00000000-00001
	2700	670	710	147	S1W0-5050277006-00000000-00001

3

### Table 2. Product Selection Guide, $I_F = 750$ mA, $T_j = 25$ °C, RH30%





## **Product Performance & Characterization Guide**

Table 3. Characteristics, I<sub>F</sub>=750mA, T<sub>j</sub>=25°C

SEOUL

Parameter	Symbol		Unit		
Farameter	Symbol	Min.	Тур.	Max.	Unit
Forward Voltage	V <sub>F</sub>	6.2	-	6.8	V
Luminous Flux	$\Phi_v^{[2]}$	670	-	820	lm
Correlated Color Temperature <sup>[3]</sup>	CCT	2,700	-	7,000	к
CRI <sup>[4]</sup>	Ra	70	-	80	-
Viewing Angle	2Θ1/2	-	120	-	deg.
Thermal resistance (J to S) <sup>[5]</sup>	Rθ <sub>j-s</sub>	-	2.9	-	K/W
ESD Sensitivity(HBM) [6]	-		Class2 JESE	022-A114E	

#### Table 4. Absolute Maximum Ratings

Parameter	Symbol	Value	Unit
Forward Current	I <sub>F</sub>	1000	mA
Power Dissipation	P <sub>D</sub>	6.8	W
Junction Temperature	Τ <sub>j</sub>	125	٥C
Operating Temperature	T <sub>opr</sub>	-40 ~ + 100	°C
Storage Temperature	T <sub>stg</sub>	-40 ~ + 100	٥C

#### Notes :

- (1) Seoul Semiconductor maintains a tolerance of  $\pm$ 7% on flux and power measurements.
- (2)  $\Phi_V$  is the total luminous flux output as measured with an integrating sphere.
- (3) Correlated Color Temperature is derived from the CIE 1931 Chromaticity diagram.
  Color coordinate : ±0.005, CCT ±5% tolerance.
- (4) Tolerance is  $\pm 2.0$  on CRI measurements.
- Calculated performance values are for reference only.
- All measurements were made under the standardized environment of Seoul Semiconductor.
- Thermal resistance can be increased substantially depending on the heat sink design/operating condition, and the maximum possible driving current will decrease accordingly.



## **Characteristics Graph**

SEOUL

Fig 1. Color Spectrum, T<sub>i</sub>=25°C, I<sub>F</sub>=750mA





Fig 2. Radiant pattern, T<sub>i</sub>=25°C, I<sub>F</sub>=750mA



S1W0-5050xx06-00000000-00001 -5050 Series

# **Characteristics Graph**

SEOUL






Fig 3. Forward Voltage vs. Forward Current, T<sub>j</sub>=25°C


Fig 4. Forward Current vs. Relative Luminous Flux, T<sub>i</sub>=25°C






# **Characteristics Graph**











# **Characteristics Graph**







# **Characteristics Graph**

SEOUL






Fig 6. Relative Light Output vs. Junction Temperature,  $I_F$ =750mA





S1W0-5050xx06-00000000-00001 -5050 Series

# **Characteristics Graph**

SEOUL




Fig 8. Junction Temp. vs. CIE X, Y Shift,  $I_F$ =750mA

S1W0-5050xx06-0000000-00001 -5050 Series

# **Characteristics Graph**

SEOUL




Fig 8. Junction Temp. vs. CIE X, Y Shift,  $I_F$ =750mA

# **Characteristics Graph**

SEOUL




Fig 9. Maximum Forward Current vs. Ambient Temperature, T<sub>j</sub>(max.)=125°C, I<sub>F</sub>=1A



### **Color Bin Structure**

#### Table 5. Bin Code description

		Color Chromaticity Coordinate	Forward Voltage (V <sub>f</sub> ) I <sub>F</sub> =750mA, T <sub>j</sub> =25℃			CRI		
Fait Nulliper	Bin Code	Min.	Max.	I <sub>F</sub> =750mA, T <sub>j</sub> =85℃	Bin Code	Min.	Max.	UNI
S1W0-	W1	670	720		Z2	6.2	6.4	
5050xxxx06- 00000000-	W2	720	770	Refer to page 14~16	Z4	6.4	6.6	70
00001	W3	770	820		Z6	6.6	6.8	

#### Table 6. Luminous Flux rank distribution

ССТ	CIE	Flux Rank			
7000 ~ 6000K	А	W1	W2	W3	
6000 ~ 5300K	В	W1	W2	W3	
5300 ~ 4700K	С	W1	W2	W3	
4700 ~ 4200K	D	W1	W2	W3	
4200 ~ 3700K	E	W1	W2	W3	
3700 ~ 3200K	F	W1	W2	W3	
3200 ~ 2900K	G	W1	W2	W3	
2900 ~ 2600K	Н	W1	W2	W3	




Available ranks Not yet available ranks

• All measurements were made under the standardized environment of Seoul Semiconductor.



### **Color Bin Structure**

CIE Chromaticity Diagram (Cool white), T<sub>i</sub>=85°C, I<sub>F</sub>=750mA



6500K 4Step		5700K 4Step		5000K 4Step	
4A		4B		4C	
Center point	0.3123 : 0.3282	Center point	0.3287 : 0.3417	Center point	0.3447 : 0.3553
Major Axis a	0.0088	Major Axis a	0.0095	Major Axis a	0.0108
Minor Axis b	0.0036	Minor Axis b	0.0040	Minor Axis b	0.0047
Ellipse Rotation Angle	58	Ellipse Rotation Angle	59	Ellipse Rotation Angle	60

6500K 5Step		5700K 5Step		5000K 5Step	
5A		5B		5C	
Center point	0.3123 : 0.3282	Center point	0.3287 : 0.3417	Center point	0.3447 : 0.3553
Major Axis a	0.0110	Major Axis a	0.0118	Major Axis a	0.0135
Minor Axis b	0.0045	Minor Axis b	0.0050	Minor Axis b	0.0058
Ellipse Rotation Angle	58	Ellipse Rotation Angle	59	Ellipse Rotation Angle	60




S1W0-5050xx06-0000000-00001 -5050 Series

### **Color Bin Structure**

SEOUL

CIE Chromaticity Diagram (Neutral white), T<sub>i</sub>=85°C, I<sub>F</sub>=750mA




4500	K 4Step	4000K 4Step			
	4D	4E			
Center point	0.3611 : 0.3658	Center point	0.3818 : 0.3797		
Major Axis a	0.0120	Major Axis a	0.0125		
Minor Axis b	0.0052	Minor Axis b	0.0053		
Ellipse Rotation Angle	55	Ellipse Rotation Angle	53		

4500	K 5Step	4000K 5Step			
	5D	5E			
Center point	0.3611 : 0.3658	Center point	0.3818 : 0.3797		
Major Axis a	0.0150	Major Axis a	0.0157		
Minor Axis b	0.0065	Minor Axis b	0.0067		
Ellipse	55	Ellipse	53		
Rotation Angle	55	Rotation Angle			

### **Color Bin Structure**

SEOUL

CIE Chromaticity Diagram (Warm white), T<sub>i</sub>=85°C, I<sub>F</sub>=750mA



3500K 5Step		3000K 5Step		2700K 5Step		
5F		5G		5H		
Center point	0.4073 : 0.3917	Center point	0.4338 : 0.4030	Center point	0.4578 : 0.4101	
Major Axis a	0.0155	Major Axis a	0.0142	Major Axis a	0.0132	
Minor Axis b	0.0068	Minor Axis b	0.0068	Minor Axis b	0.0068	
Ellipse	53	Ellipse	53	Ellipse	54	
Rotation Angle	55	Rotation Angle	tation Angle		54	


0.44




S1W0-5050xx06-00000000-00001 -5050 Series

## **Mechanical Dimensions**

< Top View >





< Side view>




#### Notes :

- (1) All dimensions are in millimeters.
- (2) Scale : none
- (3) Undefined tolerance is  $\pm 0.2 \text{mm}$



S1W0-5050xx06-0000000-00001 -5050 Series


### **Recommended Solder Pad**



#### Notes :

- (1) All dimensions are in millimeters.
- (2) Scale : none
- (3) Undefined tolerance is  $\pm 0.2$ mm
- (4) This drawing without tolerances are for reference only.

### **Reflow Soldering Characteristics**



#### Table 7.

SEOUL

Profile Feature	Sn-Pb Eutectic Assembly	Pb-Free Assembly
Average ramp-up rate ( $T_{smax}$ to $T_p$ )	3° C/second max.	3° C/second max.
Preheat - Temperature Min (T <sub>smin</sub> ) - Temperature Max (T <sub>smax</sub> ) - Time (T <sub>smin</sub> to T <sub>smax</sub> ) (t <sub>s</sub> )	100 °C 150 °C 60-120 seconds	150 °C 200 °C 60-180 seconds
Time maintained above: - Temperature (T <sub>L</sub> ) - Time (t <sub>L</sub> )	183 °C 60-150 seconds	217 °C 60-150 seconds
Peak Temperature (T <sub>p</sub> )	215℃	260°C
Time within 5°C of actual Peak Temperature (t <sub>p</sub> )2	10-30 seconds	20-40 seconds
Ramp-down Rate	6 °C/second max.	6 °C/second max.
Time 25°C to Peak Temperature	6 minutes max.	8 minutes max.


### Caution


- (1) Reflow soldering is recommended not to be done more than two times. In the case of more than 24 hours passed soldering after first, LEDs will be damaged.
- (2) Repairs should not be done after the LEDs have been soldered. When repair is unavoidable, suitable tools must be used.
- (3) Die slug is to be soldered.
- (4) When soldering, do not put stress on the LEDs during heating.
- (5) After soldering, do not warp the circuit board.



## **Emitter Tape & Reel Packaging**

SEOUL






#### Notes :

- (1) Quantity : 7 inch reel type ( 1,000 pcs / Reel  $\pm$  1pcs)
- (2) Cumulative Tolerance : Cumulative Tolerance/10 pitches to be  $\pm 0.2 \text{mm}$
- (3) Adhesion Strength of Cover Tape : Adhesion strength to be 0.1-0.7N when the cover tape is turned off from the carrier tape at the angle of 10° to the carrier tape
- (4) Package : P/N, Manufacturing data Code No. and quantity to be indicated on a damp proof Package.



S1W0-5050xx06-00000000-00001 -5050 Series

## **Emitter Tape & Reel Packaging**





SEOUL

### Table 8. Part Numbering System

Part Number Code	Description	Part Number	Value
X <sub>1</sub>	Company	S	Seoul Semiconductor
X <sub>2</sub>	Level of Integration	1	Discrete LED
X <sub>3</sub> X <sub>4</sub>	Technology	WO	White General
X <sub>5</sub> X <sub>6</sub> X <sub>7</sub> X <sub>8</sub>	Dimension	5050	5.0x5.0mm
Х <sub>9</sub> Х <sub>10</sub>	CCT XX	ХХ	65: 6500K 57: 5700K 50: 5000K 45: 4500K 40: 4000K
		~~~~	35: 3500K 30: 3000K 27: 2700K CRI70
X <sub>11</sub> X <sub>12</sub>	CRI	~~~	GRI70
X <sub>13</sub> X <sub>14</sub>	Vf	18	
X <sub>15</sub> X <sub>16</sub> X <sub>17</sub>	Characteristic code Flux Rank	000	
X <sub>18</sub> X <sub>19</sub> X <sub>20</sub>	Characteristic code Vf Rank	000	
X <sub>21</sub> X <sub>22</sub>	Characteristic code Color Step	00	
	_		
X <sub>23</sub> X <sub>24</sub>	Туре	00	
X <sub>25</sub> X <sub>26</sub> X <sub>27</sub>	Internal code	001	

SEOUL

S1W0-5050xx06-00000000-00001 -5050 Series

### Handling of Silicone Resin for LEDs

(1) During processing, mechanical stress on the surface should be minimized as much as possible. Sharp objects of all types should not be used to pierce the sealing compound.





(2) In general, LEDs should only be handled from the side. By the way, this also applies to LEDs without a silicone sealant, since the surface can also become scratched.

(3) When populating boards in SMT production, there are basically no restrictions regarding the form of the pick and place nozzle, except that mechanical pressure on the surface of the resin must be prevented. This is assured by choosing a pick and place nozzle which is larger than the LED's reflector area.

(4) Silicone differs from materials conventionally used for the manufacturing of LEDs. These conditions must be considered during the handling of such devices. Compared to standard encapsulants, silicone is generally softer, and the surface is more likely to attract dust.

As mentioned previously, the increased sensitivity to dust requires special care during processing. In cases where a minimal level of dirt and dust particles cannot be guaranteed, a suitable cleaning solution must be applied to the surface after the soldering of components.

(5) SSC suggests using isopropyl alcohol for cleaning. In case other solvents are used, it must be assured that these solvents do not dissolve the package or resin. Ultrasonic cleaning is not recommended. Ultrasonic cleaning may cause damage to the LED.

(6) Please do not mold this product into another resin (epoxy, urethane, etc) and do not handle this. product with acid or sulfur material in sealed space.



## **Precaution for Use**

#### (1) Storage

To avoid the moisture penetration, we recommend store in a dry box with a desiccant . The recommended storage temperature range is  $5^{\circ}$ C to  $30^{\circ}$ C and a maximum humidity of RH50%.

(2) Use Precaution after Opening the Packaging

Use SMT techniques properly when you solder the LED as separation of the lens may affect the light output efficiency.

Pay attention to the following:

- a. Recommend conditions after opening the package
  - Sealing / Temperature :  $5 \sim 40^{\circ}$ C Humidity : less than RH30%
- b. If the package has been opened more than 4 week(MSL\_2a) or the color of the

desiccant changes, components should be dried for 10-12hr at  $60\pm5^\circ\!C$ 

(3) Do not apply mechanical force or excess vibration during the cooling process to normal temperature after soldering.

(4) Do not rapidly cool device after soldering.

(5) Components should not be mounted on warped (non coplanar) portion of PCB.

(6) Radioactive exposure is not considered for the products listed here in.

(7) Gallium arsenide is used in some of the products listed in this publication. These products are dangerous if they are burned or shredded in the process of disposal. It is also dangerous to drink the liquid or inhale the gas generated by such products when chemically disposed of.

(8) This device should not be used in any type of fluid such as water, oil, organic solvent and etc. When washing is required, IPA (Isopropyl Alcohol) should be used.

(9) When the LEDs are in operation the maximum current should be decided after measuring the package temperature.

(10) LEDs must be stored properly to maintain the device. If the LEDs are stored for 3 months or more after being shipped from Seoul Semiconductor. A sealed container with a nitrogen atmosphere should be used for storage.

(11) The appearance and specifications of the product may be modified for improvement without notice.

(12) Long time exposure of sunlight or occasional UV exposure will cause lens discoloration.



### **Precaution for Use**

(13) VOCs (Volatile organic compounds) emitted from materials used in the construction of fixtures can penetrate silicone encapsulants of LEDs and discolor when exposed to heat and photonic energy. The result can be a significant loss of light output from the fixture. Knowledge of the properties of the materials selected to be used in the construction of fixtures can help prevent these issues.

(14) The slug is electrically isolated.

(15) Attaching LEDs, do not use adhesives that outgas organic vapor.

(16) The driving circuit must be designed to allow forward voltage only when it is ON or OFF. If the reverse voltage is applied to LED, migration can be generated resulting in LED damage.

(17) LEDs are sensitive to Electro-Static Discharge (ESD) and Electrical Over Stress (EOS). Below is a list of suggestions that Seoul Semiconductor purposes to minimize these effects.

a. ESD (Electro Static Discharge)

Electrostatic discharge (ESD) is the defined as the release of static electricity when two objects come into contact. While most ESD events are considered harmless, it can be an expensive problem in many industrial environments during production and storage. The damage from ESD to an LEDs may cause the product to demonstrate unusual characteristics such as:

- Increase in reverse leakage current lowered turn-on voltage
- Abnormal emissions from the LED at low current

The following recommendations are suggested to help minimize the potential for an ESD event. One or more recommended work area suggestions:

- Ionizing fan setup
- ESD table/shelf mat made of conductive materials
- ESD safe storage containers

One or more personnel suggestion options:

- Antistatic wrist-strap
- Antistatic material shoes
- Antistatic clothes

Environmental controls:

- Humidity control (ESD gets worse in a dry environment)



### **Precaution for Use**

b. EOS (Electrical Over Stress)

Electrical Over-Stress (EOS) is defined as damage that may occur when an electronic device is subjected to a current or voltage that is beyond the maximum specification limits of the device. The effects from an EOS event can be noticed through product performance like:

- Changes to the performance of the LED package

(If the damage is around the bond pad area and since the package is completely encapsulated the package may turn on but flicker show severe performance degradation.)

- Changes to the light output of the luminaire from component failure
- Components on the board not operating at determined drive power

Failure of performance from entire fixture due to changes in circuit voltage and current across total circuit causing trickle down failures. It is impossible to predict the failure mode of every LED exposed to electrical overstress as the failure modes have been investigated to vary, but there are some common signs that will indicate an EOS event has occurred:

- Damaged may be noticed to the bond wires (appearing similar to a blown fuse)
- Damage to the bond pads located on the emission surface of the LED package
- (shadowing can be noticed around the bond pads while viewing through a microscope)
- Anomalies noticed in the encapsulation and phosphor around the bond wires.
- This damage usually appears due to the thermal stress produced during the EOS event.

c. To help minimize the damage from an EOS event Seoul Semiconductor recommends utilizing:

- A surge protection circuit
- An appropriately rated over voltage protection device
- A current limiting device



## **Company Information**

#### Published by

Seoul Semiconductor © 2013 All Rights Reserved.

#### **Company Information**

Seoul Semiconductor (www.SeoulSemicon.com) manufacturers and packages a wide selection of light emitting diodes (LEDs) for the automotive, general illumination/lighting, Home appliance, signage and back lighting markets. The company is the world's fifth largest LED supplier, holding more than 10,000 patents globally, while offering a wide range of LED technology and production capacity in areas such as "nPola", "Acrich", the world's first commercially produced AC LED, and "Acrich MJT - Multi-Junction Technology" a proprietary family of high-voltage LEDs.

The company's broad product portfolio includes a wide array of package and device choices such as Acrich and Acirch2, high-brightness LEDs, mid-power LEDs, side-view LEDs, and through-hole type LEDs as well as custom modules, displays, and sensors.

#### Legal Disclaimer

Information in this document is provided in connection with Seoul Semiconductor products. With respect to any examples or hints given herein, any typical values stated herein and/or any information regarding the application of the device, Seoul Semiconductor hereby disclaims any and all warranties and liabilities of any kind, including without limitation, warranties of non-infringement of intellectual property rights of any third party. The appearance and specifications of the product can be changed to improve the quality and/or performance without notice.