Notice for TAIYO YUDEN products

Please read this notice before using the TAIYO YUDEN products.

/!\ REMINDERS

Product Information in this Catalog

Product information in this catalog is as of January 2021. All of the contents specified herein and production status of the products listed in this catalog are subject to change without notice due to technical improvement of our products, etc. Therefore, please check for the latest information carefully before practical application or use of our products.

Please note that TAIYO YUDEN shall not be in any way responsible for any damages and defects in products or equipment incorporating our products, which are caused under the conditions other than those specified in this catalog or individual product specification sheets.

Approval of Product Specifications

Please contact TAIYO YUDEN for further details of product specifications as the individual product specification sheets are available. When using our products, please be sure to approve our product specifications or make a written agreement on the product specification with TAIYO YUDEN in advance.

Pre-Evaluation in the Actual Equipment and Conditions

Please conduct validation and verification of our products in actual conditions of mounting and operating environment before using our products.

Limited Application

1. Equipment Intended for Use

The products listed in this catalog are intended for general-purpose and standard use in general electronic equipment (e.g., AV equipment, OA equipment, home electric appliances, office equipment, information and communication equipment including, without limitation, mobile phone, and PC) and other equipment specified in this catalog or the individual product specification sheets.

TAIYO YUDEN has the line-up of the products intended for use in automotive electronic equipment, telecommunications infrastructure and industrial equipment, or medical devices classified as GHTF Classes A to C (Japan Classes I to III). Therefore, when using our products for these equipment, please check available applications specified in this catalog or the individual product specification sheets and use the corresponding products.

2. Equipment Requiring Inquiry

Please be sure to contact TAIYO YUDEN for further information before using the products listed in this catalog for the following equipment (excluding intended equipment as specified in this catalog or the individual product specification sheets) which may cause loss of human life, bodily injury, serious property damage and/or serious public impact due to a failure or defect of the products and/or malfunction attributed thereto.

- (1) Transportation equipment (automotive powertrain control system, train control system, and ship control system, etc.)
- (2) Traffic signal equipment
- (3) Disaster prevention equipment, crime prevention equipment
- (4) Medical devices classified as GHTF Class C (Japan Class III)
- (5) Highly public information network equipment, dataprocessing equipment (telephone exchange, and base station, etc.)
- (6) Any other equipment requiring high levels of quality and/or reliability equal to the equipment listed above

3. Equipment Prohibited for Use

Please do not incorporate our products into the following equipment requiring extremely high levels of safety and/or reliability.

- (1) Aerospace equipment (artificial satellite, rocket, etc.)
- (2) Aviation equipment *1
- (3) Medical devices classified as GHTF Class D (Japan Class IV), implantable medical devices *2

- (4) Power generation control equipment (nuclear power, hydroelectric power, thermal power plant control system, etc.)
- (5) Undersea equipment (submarine repeating equipment, underwater work equipment, etc.)
- (6) Military equipment
- (7) Any other equipment requiring extremely high levels of safety and/or reliability equal to the equipment listed above

*Notes:

- 1. There is a possibility that our products can be used only for aviation equipment that does not directly affect the safe operation of aircraft (e.g., in-flight entertainment, cabin light, electric seat, cooking equipment) if such use meets requirements specified separately by TAIYO YUDEN. Please be sure to contact TAIYO YUDEN for further information before using our products for such aviation equipment.
- Implantable medical devices contain not only internal unit which is implanted in a body, but also external unit which is connected to the internal unit.

4. Limitation of Liability

Please note that unless you obtain prior written consent of TAIYO YUDEN, TAIYO YUDEN shall not be in any way responsible for any damages incurred by you or third parties arising from use of the products listed in this catalog for any equipment that is not intended for use by TAIYO YUDEN, or any equipment requiring inquiry to TAIYO YUDEN or prohibited for use by TAIYO YUDEN as described above.

Safety Design

When using our products for high safety and/or reliability-required equipment or circuits, please fully perform safety and/or reliability evaluation. In addition, please install (i) systems equipped with a protection circuit and a protection device and/or (ii) systems equipped with a redundant circuit or other system to prevent an unsafe status in the event of a single fault for a failsafe design to ensure safety.

Intellectual Property Rights

Information contained in this catalog is intended to convey examples of typical performances and/or applications of our products and is not intended to make any warranty with respect to the intellectual property rights or any other related rights of TAIYO YUDEN or any third parties nor grant any license under such rights.

Limited Warranty

Please note that the scope of warranty for our products is limited to the delivered our products themselves and TAIYO YUDEN shall not be in any way responsible for any damages resulting from a failure or defect in our products. Notwithstanding the foregoing, if there is a written agreement (e.g., supply and purchase agreement, quality assurance agreement) signed by TAIYO YUDEN and your company, TAIYO YUDEN will warrant our products in accordance with such agreement

■ TAIYO YUDEN's Official Sales Channel

The contents of this catalog are applicable to our products which are purchased from our sales offices or authorized distributors (hereinafter "TAIYO YUDEN's official sales channel"). Please note that the contents of this catalog are not applicable to our products purchased from any seller other than TAIYO YUDEN's official sales channel.

Caution for Export

Some of our products listed in this catalog may require specific procedures for export according to "U.S. Export Administration Regulations", "Foreign Exchange and Foreign Trade Control Law" of Japan, and other applicable regulations. Should you have any questions on this matter, please contact our sales staff.

[▶] This catalog contains the typical specification only due to the limitation of space. When you consider the purchase of our products, please check our product specification sheets. For details of each product (characteristics graph, reliability information, precautions for use, and so on), see our website (http://www.ty-top.com/).

Automotive Application Guide

We classify automotive electronic equipment into the following four application categories and set usable application categories for each of our products. When using our products for automotive electronic equipment, please be sure to check such application categories and use our products accordingly. Should you have any questions on this matter, please contact us.


Category	Automotive Electronic Equipment (Typical Example)
POWERTRAIN	 Engine ECU (Electronically Controlled Fuel Injector) Cruise Control Unit 4WS (4 Wheel Steering) Transmission Power Steering HEV/PHV/EV Core Control (Battery, Inverter, DC-DC)
SAFETY	 Automotive Locator (Car location information providing device), etc. ABS (Anti-Lock Brake System) ESC (Electronic Stability Control) Airbag ADAS (Equipment that directly controls running, turning and stopping), etc.
BODY & CHASSIS	Wiper Automatic Door Power Window Keyless Entry System Electric Door Mirror Automobile Digital Mirror Interior Lighting Automobile Air Conditioning System LED Headlight TPMS (Tire Pressure Monitoring System) Anti-Theft Device (Immobilizer), etc.
INFOTAINMENT	 Car Infotainment System ITS/Telematics System Instrument Cluster ADAS (Sensor, Equipment that is not interlocked with safety equipment or powertrain) Dashcam (genuine products for automotive manufacturer), etc.

[▶] This catalog contains the typical specification only due to the limitation of space. When you consider the purchase of our products, please check our product specification sheets. For details of each product (characteristics graph, reliability information, precautions for use, and so on), see our website (http://www.ty-top.com/).

MULTILAYER CERAMIC CAPACITORS

REFLOW AEC-Q200

■PART NUMBER



1 Rated voltage

Rated voltage[VDC]
4
6.3
10
16
25
35
50
100
250
630

②Series name

_	
Code	Series name
М	Multilayer ceramic capacitor
V	Multilayer ceramic capacitor for high frequency
W	LW reverse type multilayer capacitor

3End termination

Code	End termination			
K	Plated			
J	Soft Termination			
S	Cu Internal Electrodes (For High Frequency)			
F	High Reliability Application			
R	High Reliability Application			
	(Cu External Electrodes)			

4Dimension (L × W)

Type	Dimensions (L×W)[mm]	EIA (inch)
063	0.6 × 0.3	0201
105	1.0 × 0.5	0402
105	0.52 × 1.0 💥	0204
107	1.6 × 0.8	0603
107	0.8 × 1.6 💥	0306
010	2.0 × 1.25	0805
212	1.25 × 2.0 💥	0508
316	3.2 × 1.6	1206
325	3.2 × 2.5	1210
432	4.5 × 3.2	1812
\\	/ -	

Note: ※LW reverse type(□WK) only

5Dimension tolerance

Code	Type	L[mm]	W[mm]	T[mm]
Δ	ALL	Standard	Standard	Standard
	063	0.6±0.05	0.3±0.05	0.3±0.05
	105	1.0±0.10	0.5±0.10	0.5±0.10
	107	1.6+0.15/-0.05	0.8+0.15/-0.05	0.8+0.15/-0.05
Α	212	201015/ 005	1.25+0.15/-0.05	0.85±0.10
	212	2.0+0.15/-0.05	1.25 + 0.15/ - 0.05	1.25+0.15/-0.05
	316	3.2±0.20	1.6±0.20	1.6±0.20
	325	3.2±0.30	2.5±0.30	2.5±0.30
	105	1.0+0.15/-0.05	0.5+0.15/-0.05	0.5+0.15/-0.05
	107	1.6+0.20/-0	0.8+0.20/-0	0.8+0.20/-0
В	212	2.0+0.20/-0	1.25+0.20/-0	0.85±0.10
				1.25+0.20/-0
	316	3.2±0.30	1.6±0.30	1.6±0.30
	105	1.0+0.20/-0	0.5+0.20/-0	0.5+0.20/-0
С	107	1.6+0.25/-0	0.8+0.25/-0	0.8+0.25/-0
	212	2.0+0.25/-0	1.25+0.25/-0	1.25+0.25/-0
	212	2.0±0.15	1.25±0.15	0.85±0.15
V	216	010 000	1.6±0.20	1.15±0.20
K	316	3.2±0.20		1.6±0.20
	325	3.2±0.50	2.5±0.30	2.5±0.30

Note: cf. STANDARD EXTERNAL DIMENSIONS

Δ= Blank space

6Temperature characteristics code

High dielectric type

■ High dielectric	■ High dielectric type						
Code		cable	Temperature	Ref. Temp.[°C]	Capacitance change	Capacitance	Tolerance
	stan	dard	range[°C]			tolerance	code
BJ	EIA	X5R	−55 ~ + 85	25	±15%	±10%	K
	LIA	AJI	33.4 1 83	23	上1370	±20%	М
C6	EIA	X6S	-55~+105	25	±22%	±10%	K
	LIA	703	33.4 1 103	23	± 22 70	±20%	М
В7	EIA	X7R	-55~+125	25	±15%	±10%	K
Б/	EIA	A/K	-55.4 + 125	25	±13%	±20%	М
C7	EIA	X7S	-55~+125	25	±22%	±10%	K
67	EIA	X/S	-55~+125	25	±22%	±20%	М
		FIA VIT	(37 55 1.405	0.5	1.000// 000/	±10%	K
D7	EIA	X7T	-55 ~ +125	25	+22%/-33%	±20%	М

[▶] This catalog contains the typical specification only due to the limitation of space. When you consider the purchase of our products, please check our product specification sheets. For details of each product (characteristics graph, reliability information, precautions for use, and so on), see our website (http://www.ty-top.com/).

for High Quality Equipment

■ remperature c	ompensa	ating type	e				
Code		icable idard	Temperature range[°C]	Ref. Temp.[°C]	Capacitance change	Capacitance tolerance	Tolerance code
						±0.1pF	В
	JIS	CG		20		±0.25pF	С
CG			-55~+125		0±30ppm/°C	±0.5pF	D
CG			-55.4 + 125		0±30ррш/ С	±1pF	F
	EIA	C0G		25		±2%	G
	l	I	I	I		1.50/	

7Nominal capacitance

Code (example)	Nominal capacitance
0R5	0.5pF
010	1pF
100	10pF
101	100pF
102	1,000pF
103	0.01 μ F
104	0.1 μ F
105	1.0 μ F
106	10 μ F
107	100 μ F

Note : R=Decimal point

© Capacitance tolerance

Code	Capacitance tolerance
Α	±0.05pF
В	±0.1pF
С	±0.25pF
D	±0.5pF
G	±2%
J	±5%
K	±10%
М	±20%

Thickness

Code	Thickness[mm]			
Р	0.3			
Т	0.3			
V	0.5			
С	0.7(107type or more)			
Α	0.8			
D	0.85(212type or more)			
F	1.15			
G	1.25			
L	1.6			
N	1.9			
М	2.5			

®Special code

Code	Special code
_	Standard
Н	MLCC for Automotive
8	MLCC for Telecommunications infrastructure and Industrial equipment / Medical devices


①Packaging


Code	Packaging
F	ϕ 178mm Taping (2mm pitch)
R	φ 178mm Embossed Taping (4mm pitch)
Т	ϕ 178mm Taping (4mm pitch)
	ϕ 178mm Taping (4mm pitch, 1000 pcs/reel)
Р	325 type(Thickness code M)

12Internal code

Garrest rian couc	
Code	Internal code
Δ	Standard

[▶] This catalog contains the typical specification only due to the limitation of space. When you consider the purchase of our products, please check our product specification sheets. For details of each product (characteristics graph, reliability information, precautions for use, and so on), see our website (http://www.ty-top.com/).





T / FIA)		Dime	nsion [mm] (inch)		
Type(EIA)	L	W	Т	*1	е
□MK063(0201)	0.6 ± 0.03	0.3 ± 0.03	0.3±0.03	Т	0.15±0.05
□MK003(0201)	(0.024 ± 0.001)	(0.012 ± 0.001)	(0.012±0.001)	'	(0.006 ± 0.002)
□MK105(0402)	1.0±0.05	0.5 ± 0.05	0.5±0.05	V	0.25±0.10
□MF105(0402)	(0.039 ± 0.002)	(0.020 ± 0.002)	(0.020 ± 0.002)	٧	(0.010 ± 0.004)
□WK105(0204)※	0.52±0.05	1.0±0.05	0.3±0.05	Р	0.18±0.08
□WK103(0204)%	(0.020 ± 0.002)	(0.039 ± 0.002)	(0.012 ± 0.002)	Г	(0.007 ± 0.003)
□MK107(0603)	1.6±0.10	0.8 ± 0.10	0.8±0.10	Α	0.35±0.25
□MF107(0603)	(0.063 ± 0.004)	(0.031 ± 0.004)	(0.031 ± 0.004)	_ A	(0.014 ± 0.010)
□MJ107(0603)	1.6±0.10	0.8 ± 0.10	0.8±0.10	Α	0.35 + 0.3 / -0.25
□MJ107(0603)	(0.063 ± 0.004)	(0.031 ± 0.004)	(0.031 ± 0.004)	А	(0.014 + 0.012 / -0.010)
□VS107(0603)	1.6±0.10	0.8±0.10	0.7±0.10	С	0.35±0.25
□ √5107(0603)	(0.063 ± 0.004)	(0.031 ± 0.004)	(0.028 ± 0.004)		(0.014 ± 0.010)
□WK107(0306)%	0.8±0.10	1.6±0.10	0.5±0.05	V	0.25±0.15
□WK107(0306)※	(0.031 ± 0.004)	(0.063 ± 0.004)	(0.020 ± 0.002)	V	(0.010 ± 0.006)
			0.85±0.10	_	
□MK212(0805)	2.0±0.10	1.25±0.10	(0.033 ± 0.004)	D	0.5±0.25
□MF212(0805)	(0.079 ± 0.004)	(0.049 ± 0.004)	1.25±0.10	_	(0.020 ± 0.010)
			(0.049 ± 0.004)	G	
			0.85±0.10	_	
TM 1040 (0005)	2.0±0.10	1.25±0.10	(0.033 ± 0.004)	D	0.5 + 0.35 / -0.25
□MJ212(0805)	(0.079 ± 0.004)	(0.049 ± 0.004)	1.25±0.10		(0.020 + 0.014 / -0.010)
			(0.049 ± 0.004)	G	
(D)(0010(000F)	2.0±0.10	1.25±0.10	0.85±0.10	_	0.5±0.25
□VS212(0805)	(0.079 ± 0.004)	(0.049 ± 0.004)	(0.033 ± 0.004)	D	(0.020 ± 0.010)
□WK010(0E00)\%	1.25±0.15	2.0±0.15	0.85±0.10		0.3±0.2
□WK212(0508)※	(0.049 ± 0.006)	(0.079 ± 0.006)	(0.033 ± 0.004)	D	(0.012 ± 0.008)
			1.15±0.10	_	
□MK316(1206)	3.2±0.15	1.6±0.15	(0.045 ± 0.004)	F	0.5 + 0.35 / -0.25
□MF316(1206)	(0.126 ± 0.006)	(0.063 ± 0.006)	1.6±0.20		(0.020 + 0.014 / -0.010)
			(0.063 ± 0.008)	L	
			1.15±0.10		
	3.2±0.15	1.6±0.15	(0.045 ± 0.004)	F	0.6 + 0.4 / -0.3
□MJ316 (1206)	(0.126±0.006)	(0.063±0.006)	1.6±0.20		(0.024+0.016/-0.012)
	(,,	(0.063 ± 0.008)	L	(,
			1.15±0.10		
			(0.045 ± 0.004)	F	
□MK325(1210)	3.2±0.30	2.5±0.20	1.9±0.20		0.6±0.3
□MF325(1210)	(0.126±0.012)	(0.098±0.008)	(0.075 ± 0.008)	N	(0.024 ± 0.012)
	(0.1.20 = 0.0.12)	(0.000 = 0.000)	2.5±0.20		(0.02 1 = 0.0 12)
			(0.098 ± 0.008)	М	
			1.9±0.20		
	3.2±0.30	2.5±0.20	(0.075±0.008)	N	0.6 + 0.4 / -0.3
□MJ325(1210)	(0.126±0.012)	(0.098±0.008)	2.5±0.20		(0.024 + 0.016 / -0.012)
	(5.120 = 5.512)	(5.555 = 5.556)	(0.098 ± 0.008)	М	(5.5211 5.515) 5.012)
	4.5±0.40	3.2±0.30	2.5±0.20		0.9±0.6
□MK432(1812)	(0.177±0.016)	(0.126 ± 0.012)	(0.098±0.008)	М	(0.035 ± 0.024)
	= 5.5.07	,	(3.000 = 0.000)	1	(0.000 = 0.01 .)

Note: X. LW reverse type, *1.Thickness code

[▶] This catalog contains the typical specification only due to the limitation of space. When you consider the purchase of our products, please check our product specification sheets. For details of each product (characteristics graph, reliability information, precautions for use, and so on), see our website (http://www.ty-top.com/).

STANDARD QUANTITY

T	FIA (:)	Dime	nsion	Standard qu	uantity[pcs]
Туре	EIA (inch)	[mm]	Code	Paper tape	Embossed tape
063	0201	0.3	Т	15000	_
105	0402	0.5	V	10000	
105	0204 ※	0.30	Р	10000	_
		0.7	С	4000	
		0.8	А	4000	_
107	0603	0.8	А	3000 (Soft Termination)	_
		0.8	А	_	3000 (Soft Termination
	0306 ※	0.50	V	_	4000
		0.85	D	4000	_
	0805	1.25	G	_	3000
212	0803	1.25	G	_	2000 (Soft Termination
	0508 ※	0.85	D	4000	_
316	1006	1.15	F	_	3000
310	1206	1.6	L	_	2000
		1.15	F		2000
325	1210	1.9	N	_	2000
		2.5	М	_	500(T), 1000(P)
432	1812	2.5	M	_	500

Note : ※.LW Reverse type(□WK)

[▶] This catalog contains the typical specification only due to the limitation of space. When you consider the purchase of our products, please check our product specification sheets. For details of each product (characteristics graph, reliability information, precautions for use, and so on), see our website (http://www.ty-top.com/).

- · All the Multilayer Ceramic Capacitors of the catalog lineup are RoHS compliant
- Capacitance tolerance code is applied to ☐ of part number
- · All the Multilayer Ceramic Capacitors in the catalog lineup are applicable for reflow-soldering.

Notes)

- . The exchange of individual specifications is necessary depending on your application and/or circuit condition. Please contact TAIYO YUDEN's official sales channel.
- For Automotive (AEC-Q200 Qualified) products for BODY & CHASSIS, and INFOTAINMENT. Please check "Automotive Application Guide" for further details before using the products.

All the Multilayer Ceramic Capacitors for Automotive products are tested based on the test conditions and methods defined in AEC-Q200 by family item.

125°C products: AEC-Q200 Grade1 (we conduct the evaluation at the test condition of Grade1.)

105°C products: AEC-Q200 Grade2 (we conduct the evaluation at the test condition of Grade2.)

 85°C products: AEC-Q200 Grade3 (we conduct the evaluation at the test condition of Grade3.)

Please consult with TAIYO YUDEN's official sales channel for the details of the product specifications and AEC-Q200 test results, etc., and please review and approve the product specifications before ordering.

**1: For standard case size, please kindly refer to @Dimension, @Dimension tolerance, @Thickness and STANDARD EXTERNAL DIMENSIONS.

Multilayer Ceramic Capacitors (High dielectric type)

●063TYPE (Demension:0.6 × 0.3mm JIS:1005 EIA:0402)

[Temperature Characteristic B7 : X7R($-55\sim+125^{\circ}$ C)] 0.3mm thickness(T)

Part number 1	Part number 2	Rated voltage	Temperature	Capacitance	Capacitance	tan δ	HTLT	Thickness*1 [mm]	Note
Part number 1	Part number 2	[V]	characteristics	[F]	tolerance [%]	[%]	Rated voltage x %	Inickness [mm]	Note
TMK063 B7101∏PHFE			X7R	100 p	±10, ±20	3.5	200	0.3±0.03	
TMK063 B7151□PHFE		7	X7R	150 p	±10, ±20	3.5	200	0.3 ± 0.03	
TMK063 B7221 PHFE		7	X7R	220 p	±10, ±20	3.5	200	0.3±0.03	
TMK063 B7331 PHFE		7	X7R	330 р	±10, ±20	3.5	200	0.3±0.03	
TMK063 B7471☐PHFE		25	X7R	470 p	±10, ±20	3.5	200	0.3 ± 0.03	
TMK063 B7102∏PHFE			X7R	1000 p	±10, ±20	3.5	200	0.3 ± 0.03	
TMK063 B7152□PHFE			X7R	1500 p	±10, ±20	5	200	0.3 ± 0.03	
TMK063 B7222□PHFE			X7R	2200 p	±10, ±20	5	200	0.3 ± 0.03	
TMK063 B7332 PHFE			X7R	3300 p	±10, ±20	5	200	0.3 ± 0.03	
EMK063 B7101 PHFE			X7R	100 p	±10, ±20	3.5	200	0.3 ± 0.03	
EMK063 B7151 PHFE			X7R	150 p	±10, ±20	3.5	200	0.3 ± 0.03	
EMK063 B7221□PHFE			X7R	220 p	±10, ±20	3.5	200	0.3 ± 0.03	
EMK063 B7331 ☐ PHFE			X7R	330 p	±10, ±20	3.5	200	0.3 ± 0.03	
EMK063 B7471 PHFE		16	X7R	470 p	±10, ±20	3.5	200	0.3 ± 0.03	
EMK063 B7102 PHFE			X7R		±10, ±20	3.5	200	0.3 ± 0.03	
EMK063 B7152 PHFE			X7R	1500 p	±10, ±20	5	200	0.3 ± 0.03	
EMK063 B7222 PHFE			X7R	2200 p	±10, ±20	5	200	0.3 ± 0.03	
EMK063 B7332∏PHFE			X7R	3300 р	±10, ±20	5	200	0.3 ± 0.03	
LMK063 B7101 PHFE		_	X7R		±10, ±20	3.5	200	0.3 ± 0.03	
LMK063 B7151 PHFE			X7R		±10, ±20	3.5	200	0.3 ± 0.03	
LMK063 B7221 PHFE			X7R	220 p	±10, ±20	3.5	200	0.3 ± 0.03	
LMK063 B7331□PHFE			X7R	330 р	±10, ±20	3.5	200	0.3 ± 0.03	
LMK063 B7471 PHFE			X7R	470 p	±10, ±20	3.5	200	0.3 ± 0.03	
LMK063 B7102 PHFE		10	X7R	1000 p	±10, ±20	3.5	200	0.3 ± 0.03	
LMK063 B7152 PHFE			X7R	1500 p	±10, ±20	5	200	0.3 ± 0.03	
LMK063 B7222 PHFE		_	X7R		±10, ±20	5	200	0.3±0.03	
LMK063 B7332□PHFE		」	X7R		±10, ±20	5	200	0.3 ± 0.03	
LMK063 B7472 PHFE		」	X7R		±10, ±20	5	200	0.3 ± 0.03	
LMK063 B7682∏PHFE		」	X7R		±10, ±20	5	200	0.3 ± 0.03	
LMK063 B7103 PHFE			X7R	0.01 μ	±10, ±20	5	200	0.3 ± 0.03	

[▶] This catalog contains the typical specification only due to the limitation of space. When you consider the purchase of our products, please check our product specification sheets. For details of each product (characteristics graph, reliability information, precautions for use, and so on), see our website (http://www.ty-top.com/).

PART NUMBER

■105TYPE (Dimension:1.0 × 0.5mm JIS:1005 EIA:0402)

[Temperature Characteristic BJ : $X5R(-55 \sim +85^{\circ}C)$] 0.5mm thickness(V)

Part number 1	Part number 2	Rated voltage	Temper		Capacitance	Capacitance	$ an\delta$	HTLT	Thickness*1 [mm]	Note
T at Chamber 1	T art number 2	[V]	characte	ristics	[F]	tolerance [%]	[%]	Rated voltage x %	Thickness [illing	Note
UMK105 BJ471 UHF				X5R	470 p	±10, ±20	2.5	200	0.5 ± 0.05	
UMK105 BJ102□VHF				X5R	1000 p	±10, ±20	2.5	200	0.5 ± 0.05	
UMK105 BJ152 VHF				X5R	1500 p	±10, ±20	2.5	200	0.5 ± 0.05	
UMK105 BJ222 VHF				X5R	2200 p	$\pm 10, \pm 20$	2.5	200	0.5 ± 0.05	
UMK105 BJ332□VHF				X5R	3300 p	±10, ±20	2.5	200	0.5 ± 0.05	
UMK105 BJ472 VHF		50		X5R	4700 p	±10, ±20	2.5	200	0.5 ± 0.05	
UMK105 BJ682∏VHF				X5R	6800 p	±10, ±20	2.5	150	0.5 ± 0.05	
UMK105 BJ103[VHF				X5R	0.01 μ	±10, ±20	3.5	200	0.5 ± 0.05	
UMK105 BJ223 VHF				X5R	0.022 μ	±10, ±20	5	200	0.5 ± 0.05	
UMK105 BJ473[VHF				X5R	0.047 μ	±10, ±20	5	200	0.5 ± 0.05	
UMK105 BJ104∏VHF				X5R	0.1 μ	±10, ±20	10	150	0.5 ± 0.05	
TMK105 BJ472∏VHF				X5R	4700 p	±10, ±20	2.5	200	0.5±0.05	
TMK105 BJ682□VHF				X5R	6800 p	±10, ±20	2.5	200	0.5±0.05	
TMK105 BJ103 UHF				X5R	0.01 μ	±10, ±20	3.5	200	0.5±0.05	
TMK105 BJ153 VHF				X5R	0.015 μ	$\pm 10, \pm 20$	3.5	200	0.5 ± 0.05	
TMK105 BJ223 UHF		25		X5R	0.022 μ	$\pm 10, \pm 20$	3.5	200	0.5 ± 0.05	
TMK105 BJ333 UHF		25		X5R	0.033 μ	±10, ±20	3.5	150	0.5 ± 0.05	
TMK105 BJ473□VHF				X5R	0.047 μ	±10, ±20	3.5	150	0.5 ± 0.05	
TMK105 BJ104[]VHF				X5R	0.1 μ	±10, ±20	5	150	0.5 ± 0.05	
TMK105 BJ224 VHF				X5R	0.22 μ	±10, ±20	10	150	0.5 ± 0.05	
TMK105ABJ474 VHF				X5R	0.47 μ	±10, ±20	10	150	0.5±0.10	
EMK105 BJ103 VHF				X5R	0.01 μ	±10, ±20	3.5	200	0.5 ± 0.05	
EMK105 BJ153[]VHF				X5R	0.015 μ	±10, ±20	3.5	200	0.5±0.05	
EMK105 BJ223∏VHF				X5R	0.022 μ	±10, ±20	3.5	200	0.5 ± 0.05	
EMK105 BJ333∏VHF				X5R	0.033 μ	±10, ±20	3.5	150	0.5±0.05	
EMK105 BJ473 VHF		16		X5R	0.047 μ	±10, ±20	3.5	150	0.5±0.05	
EMK105 BJ104 VHF				X5R	0.1 μ	±10, ±20	5	150	0.5±0.05	
EMK105 BJ224 VHF				X5R	0.22 μ	±10, ±20	10	150	0.5±0.05	
EMK105ABJ474[]VHF				X5R	0.47 μ	±10, ±20	10	150	0.5±0.10	
EMK105 BJ105∏VHF				X5R	1 μ	±10, ±20	10	150	0.5±0.05	
LMK105 BJ333 VHF				X5R	0.033 μ	±10, ±20	3.5	150	0.5±0.05	
LMK105 BJ473 VHF				X5R	0.047 μ	±10, ±20	3.5	150	0.5±0.05	
LMK105 BJ104 VHF				X5R	0.1 μ	±10, ±20	5	150	0.5±0.05	
LMK105 BJ224 VHF		10		X5R	0.22 μ	±10, ±20	5	150	0.5±0.05	
LMK105ABJ474 VHF				X5R	0.47 μ	±10, ±20	10	150	0.5±0.10	
LMK105 BJ105 VHF				X5R	1 μ	±10, ±20	10	150	0.5±0.05	
LMK105ABJ225 VHF				X5R	2.2 μ	±10, ±20	10	150	0.5±0.10	
JMK105 BJ104[]VHF				X5R	0.1 μ	±10, ±20	5	150	0.5±0.05	
JMK105 BJ224 VHF				X5R	0.22 μ	±10, ±20	5	150	0.5±0.05	
JMK105 BJ474 VHF		6.3		X5R	0.47 μ	±10, ±20	10	150	0.5±0.05	
JMK105 BJ105∏VHF		0.3		X5R	1 μ	±10, ±20	10	150	0.5±0.05	
JMK105 BJ225∏VHF				X5R	2.2 μ	±10, ±20	10	150	0.5±0.05	
JMK105BBJ475MVHF			i	X5R	4.7 μ	±20	10	150	0.5+0.15/-0.05	
AMK105 BJ225∏VHF		4		X5R	2.2 μ	±10, ±20	10	150	0.5±0.05	
AMK105BBJ475MVHF		4		X5R	4.7 μ	±20	10	150	0.5+0.15/-0.05	

[▶] This catalog contains the typical specification only due to the limitation of space. When you consider the purchase of our products, please check our product specification sheets. For details of each product (characteristics graph, reliability information, precautions for use, and so on), see our website (http://www.ty-top.com/).

[Temperature Characteristic B7 : X7R($-55\sim+125^{\circ}$ C), D7 : X7T($-55\sim+125^{\circ}$ C)] 0.5mm thickness(V)

Temperature Charac	teristic B7 : X7R(-	-55 ~ +125℃	C), D7:	X7T(-	·55~+125℃)】	0.5mm thicknes	s(V)			
D. d	Part number 2	Rated voltage	Tempe	rature	Capacitance	Capacitance	tan δ	HTLT	*1	Maka
Part number 1	Part number 2	[V]	charact	eristics	[F]	tolerance [%]	[%]	Rated voltage x %	Thickness*1 [mm]	Note
UMK105 B7221 UHF				X7R	220 p	±10, ±20	2.5	200	0.5±0.05	
UMK105 B7331 VHF				X7R	330 р	±10, ±20	2.5	200	0.5 ± 0.05	
UMK105 B7471 UHF				X7R	470 p	±10, ±20	2.5	200	0.5±0.05	
UMK105 B7681 UHF				X7R	680 p	±10, ±20	2.5	200	0.5±0.05	
UMK105 B7102 UHF				X7R	1000 p	±10, ±20	2.5	200	0.5±0.05	
UMK105 B7152 UHF				X7R	1500 p	±10, ±20	2.5	200	0.5±0.05	
UMK105 B7222 UHF				X7R	2200 p	±10, ±20	2.5	200	0.5±0.05	
UMK105 B7332 UHF		F0		X7R	3300 р	±10, ±20	2.5	200	0.5±0.05	
UMK105 B7472 UHF		50		X7R	4700 p	±10, ±20	2.5	150	0.5±0.05	
UMK105 B7682 UHF		1		X7R	6800 p	±10, ±20	2.5	150	0.5±0.05	
UMK105 B7103 UHF		1		X7R	0.01 μ	±10, ±20	3.5	150	0.5±0.05	
UMK105 B7153 VHFE		1		X7R	0.015 μ	±10, ±20	3.5	200	0.5±0.05	
UMK105 B7223 UHF		1		X7R	0.022 μ	±10, ±20	10	200	0.5±0.05	
UMK105 B7333 UHFE		1		X7R	0.033 μ	±10, ±20	3.5	150	0.5±0.05	
UMK105 B7473 UHF		1		X7R	0.047 μ	±10, ±20	10	200	0.5±0.05	
UMK105 B7104 UHF		1		X7R	0.1 μ	±10, ±20	10	150	0.5±0.05	
TMK105 B7472[]VHF				X7R	4700 p	±10, ±20	2.5	200	0.5±0.05	
TMK105 B7682 VHF				X7R	6800 p	±10, ±20	2.5	200	0.5±0.05	
TMK105 B7103[VHF				X7R	0.01 μ	±10, ±20	3.5	200	0.5±0.05	
TMK105 B7153[VHF				X7R	0.015 μ	±10, ±20	3.5	150	0.5±0.05	
TMK105 B7223[]VHF		25		X7R	0.022 μ	±10, ±20	3.5	150	0.5±0.05	
TMK105 B7333 VHF		1		X7R	0.033 μ	±10, ±20	3.5	150	0.5±0.05	
TMK105 B7473∏VHF				X7R	0.047 μ	±10, ±20	3.5	150	0.5±0.05	
TMK105 B7104 VHF				X7R	0.1 μ	±10, ±20	10	150	0.5±0.05	
EMK105 B7103 VHF				X7R	0.01 μ	±10, ±20	3.5	200	0.5±0.05	
EMK105 B7153[VHF		1		X7R	0.015 μ	±10, ±20	3.5	150	0.5±0.05	
EMK105 B7223 VHF		1		X7R	0.022 μ	±10, ±20	3.5	150	0.5±0.05	
EMK105 B7333 VHF		16		X7R	0.033 μ	±10, ±20	3.5	150	0.5±0.05	
EMK105 B7473 VHF				X7R	0.047 μ	±10, ±20	3.5	150	0.5±0.05	
EMK105 B7104 VHF				X7R	0.1 μ	±10, ±20	5	150	0.5±0.05	
EMK105 B7224[]VHF				X7R	0.22 μ	±10, ±20	10	150	0.5±0.05	
LMK105 B7473[]VHF				X7R	0.047 μ	±10, ±20	3.5	150	0.5±0.05	
LMK105 B7104[]VHF		10		X7R	0.1 μ	±10, ±20	5	150	0.5±0.05	
LMK105 B7224[]VHF		1 !		X7R	0.22 μ	±10, ±20	10	150	0.5±0.05	
JMK105 B7104[]VHF				X7R	0.1 μ	±10, ±20	5	150	0.5±0.05	
JMK105 B7224[]VHF		1		X7R	0.22 μ	±10, ±20	10	150	0.5±0.05	
JMK105 B7474[]VHF		6.3		X7R	0.47 μ	±10, ±20	10	150	0.5±0.05	
JMK105CD7105[]VHF		1		X7T	1 μ	±10, ±20	10	150	0.5+0.20/-0	
AMK105 B7474 VHF		4		X7R	0.47 μ	±10, ±20	10	150	0.5±0.05	
AMINITOS D/4/4[[VIII		4		A/I\	υ.41 μ	±10, ±20	10	100	0.0 ± 0.00	

[▶] This catalog contains the typical specification only due to the limitation of space. When you consider the purchase of our products, please check our product specification sheets. For details of each product (characteristics graph, reliability information, precautions for use, and so on), see our website (http://www.ty-top.com/).

PART NUMBER

●107TYPE (Dimension:1.6 × 0.8mm JIS:1608 EIA:0603)

[Temperature Characteristic BJ : $X5R(-55\sim+85^{\circ}C)$] 0.8mm thickness(A)

Part number 1	Part number 2	Rated voltage [V]	erature teristics	Capacitance [F]	Capacitance tolerance [%]	tan δ [%]	HTLT Rated voltage x %	Thickness*1 [mm]	Note
UMK107 BJ104□AHT			X5R	0.1 μ	±10, ±20	3.5	150	0.8±0.10	
UMK107 BJ224 AHT		50	X5R	0.22 μ	±10, ±20	10	150	0.8 ± 0.10	
UMK107 BJ474□AHT		30	X5R	0.47 μ	±10, ±20	10	150	0.8 ± 0.10	<u>.</u>
UMK107ABJ105∏AHT			X5R	1 μ	±10, ±20	10	150	0.8+0.15/-0.05	<u>.</u>
GMK107 BJ223[]AHT			X5R	0.022 μ	±10, ±20	2.5	200	0.8±0.10	
GMK107 BJ473[AHT			X5R	0.047 μ	±10, ±20	3.5	200	0.8±0.10	<u>.</u>
GMK107 BJ104[AHT		35	X5R	0.1 μ	±10, ±20	3.5	150	0.8±0.10	
GMK107 BJ224 AHT		35	X5R	0.22 μ	±10, ±20	10	150	0.8±0.10	<u>.</u>
GMK107ABJ474[]AHT			X5R	0.47 μ	±10, ±20	10	150	0.8+0.15/-0.05	
GMK107 BJ105[AHT			X5R	1 μ	±10, ±20	10	150	0.8±0.10	
TMK107 BJ223∏AHT			X5R	0.022 μ	±10, ±20	2.5	200	0.8±0.10	
TMK107 BJ473∏AHT		1	X5R	0.047 μ	±10, ±20	3.5	200	0.8±0.10	
TMK107 BJ104∏AHT		1	X5R	0.1 μ	±10, ±20	3.5	150	0.8±0.10	
TMK107 BJ224□AHT		25	X5R	0.22 μ	±10, ±20	5	150	0.8±0.10	
TMK107 BJ474□AHT			X5R	0.47 μ	±10, ±20	3.5	150	0.8±0.10	
TMK107 BJ105□AHT			X5R	1 μ	±10, ±20	10	150	0.8 ± 0.10	
TMK107BBJ225[]AHT			X5R	2.2 μ	±10, ±20	10	150	0.8+0.20/-0	
EMK107 BJ104□AHT			X5R	0.1 μ	±10, ±20	3.5	150	0.8 ± 0.10	
EMK107 BJ224□AHT			X5R	0.22 μ	±10, ±20	5	150	0.8 ± 0.10	
EMK107 BJ474 AHT		16	X5R	0.47 μ	±10, ±20	3.5	150	0.8 ± 0.10	
EMK107 BJ105∏AHT		10	X5R	1 μ	±10, ±20	5	150	0.8 ± 0.10	
EMK107ABJ225∏AHT		1	X5R	2.2 μ	±10, ±20	10	150	0.8+0.15/-0.05	
EMK107BBJ475∏AHT		1	X5R	4.7 μ	±10, ±20	10	150	0.8+0.20/-0	
LMK107 BJ474[]AHT			X5R	0.47 μ	±10, ±20	3.5	150	0.8 ± 0.10	
LMK107 BJ105∏AHT		1	X5R	1 μ	±10, ±20	5	150	0.8±0.10	
LMK107 BJ225∏AHT		10	X5R	2.2 μ	±10, ±20	10	150	0.8 ± 0.10	<u>.</u>
LMK107 BJ475[AHT		1	X5R	4.7 μ	±10, ±20	10	150	0.8±0.10	
LMK107BBJ106MAHT			X5R	10 μ	±20	10	150	0.8+0.20/-0	<u>.</u>
JMK107 BJ105∏AHT			X5R	1 μ	±10, ±20	5	150	0.8 ± 0.10	
JMK107 BJ225∏AHT			X5R	2.2 μ	±10, ±20	10	150	0.8 ± 0.10	
JMK107 BJ475∏AHT		6.3	X5R	4.7 μ	±10, ±20	10	150	0.8±0.10	
JMK107ABJ106□AHT]	X5R	10 μ	±10, ±20	10	150	0.8+0.15/-0.05	
AMK107ABJ106∏AHT		4	X5R	10 μ	±10, ±20	10	150	0.8+0.15/-0.05	
AMK107BBJ226MAHT] 4	X5R	22 μ	±20	10	150	0.8+0.20/-0	

 $\begin{tabular}{l} \textbf{[} Temperature Characteristic B7: X7R(-55 \buildrel + 125 \buildrel + 125 \buildrel Characteristic B7: X7R(-55 \buildrel + 125 \buildrel + 125 \buildrel Characteristic B7: X7R(-55 \buildrel + 125 \buildre$

Part number 1	Part number 2	Rated voltage	Temperature	Capacitance	Capacitance	$ an\delta$	HTLT	Thickness*1 [mm]	Note
Fart number 1	Fart Humber 2	[V]	characteristics	[F]	tolerance [%]	[%]	Rated voltage x %	Thickness [mm]	Note
UMK107 B7102∏AHT			X7R	1000 p	±10, ±20	3.5	200	0.8±0.10	
UMK107 B7152[AHT			X7R	1500 p	±10, ±20	3.5	200	0.8 ± 0.10	
UMK107 B7222[AHT			X7R	2200 p	±10, ±20	3.5	200	0.8 ± 0.10	
UMK107 B7332[AHT			X7R	3300 p	±10, ±20	3.5	200	0.8±0.10	
UMK107 B7472[AHT			X7R	4700 p	±10, ±20	3.5	200	0.8±0.10	
UMK107 B7682[AHT			X7R	6800 p	±10, ±20	3.5	200	0.8±0.10	
UMK107 B7103[]AHT			X7R	0.01 μ	±10, ±20	3.5	200	0.8±0.10	
UMK107 B7153[]AHT		50	X7R	0.015 μ	±10, ±20	3.5	200	0.8±0.10	
UMK107 B7223[]AHT			X7R	0.022 μ	±10, ±20	3.5	200	0.8±0.10	
UMK107 B7333[AHT			X7R	0.033 μ	±10, ±20	3.5	200	0.8±0.10	
UMK107 B7473[]AHT			X7R	0.047 μ	±10, ±20	3.5	200	0.8±0.10	
UMK107 B7683[]AHT			X7R	0.068 μ	±10, ±20	3.5	150	0.8±0.10	
UMK107 B7104[]AHT			X7R	0.1 μ	±10, ±20	3.5	200	0.8±0.10	
UMK107AC7154[AHTE			X7S	0.15 μ	±10, ±20	3.5	150	0.8+0.15/-0.05	
UMK107 C7224 AHTE			X7S	0.22 μ	±10, ±20	3.5	150	0.8±0.10	
GMK107 B7473[AHT			X7R	0.047 μ	±10, ±20	3.5	200	0.8±0.10	
GMK107 B7104[]AHT			X7R	0.1 μ	±10, ±20	3.5	150	0.8±0.10	
GMK107 B7224[]AHT		35	X7R	0.22 μ	±10, ±20	10	150	0.8±0.10	
GMK107 B7474[]AHT			X7R	0.47 μ	±10, ±20	10	150	0.8±0.10	
GMK107AB7105[]AHT			X7R	1 μ	±10, ±20	10	150	0.8+0.15/-0.05	
TMK107 B7223[]AHT			X7R	0.022 μ	±10, ±20	2.5	200	0.8±0.10	
TMK107 B7473[]AHT		1	X7R	0.047 μ	±10, ±20	3.5	200	0.8±0.10	
TMK107 B7104[]AHT		25	X7R	0.1 μ	±10, ±20	3.5	150	0.8±0.10	
TMK107 B7224[]AHT		25	X7R	0.22 μ	±10, ±20	10	150	0.8±0.10	
TMK107 B7474[]AHT			X7R	0.47 μ	±10, ±20	10	150	0.8±0.10	
TMK107AB7105∏AHT			X7R	1 μ	±10, ±20	10	150	0.8+0.15/-0.05	
EMK107 B7473[]AHT			X7R	0.047 μ	±10, ±20	3.5	200	0.8±0.10	
EMK107 B7104[]AHT			X7R	0.1 μ	±10, ±20	3.5	150	0.8±0.10	
EMK107 B7224 AHT		16	X7R	0.22 μ	±10, ±20	5	150	0.8±0.10	
EMK107 B7474 AHT			X7R	0.47 μ	±10, ±20	10	150	0.8±0.10	
EMK107 B7105∏AHT			X7R	1 μ	±10, ±20	10	150	0.8±0.10	
LMK107 B7224[]AHT			X7R	0.22 μ	±10, ±20	5	150	0.8±0.10	
LMK107 B7474[AHT		10	X7R	0.47 μ	±10, ±20	3.5	150	0.8±0.10	
LMK107 B7105[AHT		10	X7R	1 μ	±10, ±20	10	150	0.8±0.10	
LMK107BD7225 AHT		1	X7T	2.2 μ	±10, ±20	10	200	0.8+0.20/-0	
JMK107 B7105∏AHT		6.3	X7R	1 μ	±10, ±20	10	150	0.8±0.10	
JMK107 B7225∏AHTR		0.3	X7R	2.2 μ	±10, ±20	10	150	0.8±0.10	

[▶] This catalog contains the typical specification only due to the limitation of space. When you consider the purchase of our products, please check our product specification sheets. For details of each product (characteristics graph, reliability information, precautions for use, and so on), see our website (http://www.ty-top.com/).

212TYPE (Dimension:2.0 × 1.25mm JIS:2012 EIA:0805)

[Temperature Characteristic BJ : $X5R(-55 \sim +85^{\circ}C)$] 1.25mm thickness(G)

Part number 1	Part number 2	Rated voltage	Tempe	erature	Capacitance	Capacitance	tan δ	HTLT	Thickness*1 [mm]	Note
rart number i	Fart number 2	[V]	charact	teristics	[F]	tolerance [%]	[%]	Rated voltage x %	Inickness [IIIII]	Note
UMK212 BJ104 GHT				X5R	0.1 μ	±10, ±20	3.5	200	1.25±0.10	
UMK212 BJ224 GHT		50		X5R	0.22 μ	±10, ±20	3.5	200	1.25±0.10	
UMK212 BJ474 GHT		50		X5R	0.47 μ	±10, ±20	3.5	150	1.25±0.10	
UMK212 BJ105[]GHT		1		X5R	1 μ	±10, ±20	5	150	1.25±0.10	
GMK212 BJ104∏GHT				X5R	0.1 μ	±10, ±20	3.5	200	1.25±0.10	
GMK212 BJ224 GHT				X5R	0.22 μ	±10, ±20	3.5	150	1.25±0.10	
GMK212 BJ474 GHT		35		X5R	0.47 μ	±10, ±20	3.5	150	1.25±0.10	
GMK212 BJ105 GHT				X5R	1 μ	±10, ±20	5	150	1.25±0.10	
GMK212BBJ225[]GHT				X5R	2.2 μ	±10, ±20	10	150	1.25+0.20/-0	
TMK212 BJ104[]GHT				X5R	0.1 μ	±10, ±20	3.5	200	1.25±0.10	
TMK212 BJ224 GHT				X5R	0.22 μ	±10, ±20	3.5	150	1.25±0.10	
TMK212 BJ474[]GHT]		X5R	0.47 μ	±10, ±20	3.5	200	1.25±0.10	
TMK212 BJ105[]GHT		25		X5R	1 μ	±10, ±20	3.5	150	1.25±0.10	
TMK212 BJ225[]GHT				X5R	2.2 μ	±10, ±20	5	150	1.25±0.10	
TMK212BBJ475[]GHT				X5R	4.7 μ	±10, ±20	10	150	1.25+0.20/-0	
TMK212BBJ106 GHT				X5R	10 μ	±10, ±20	10	150	1.25+0.20/-0	
EMK212 BJ105[]GHT				X5R	1 μ	±10, ±20	3.5	150	1.25±0.10	
EMK212 BJ225 GHT		16		X5R	2.2 μ	±10, ±20	5	150	1.25±0.10	
EMK212ABJ475[]GHT		10		X5R	4.7 μ	±10, ±20	10	150	1.25+0.15/-0.05	
EMK212BBJ106[]GHT				X5R	10 μ	±10, ±20	10	150	1.25+0.20/-0	
LMK212 BJ225 GHT				X5R	2.2 μ	±10, ±20	5	200	1.25±0.10	
LMK212ABJ475[]GHT		10		X5R	4.7 μ	±10, ±20	10	150	1.25+0.15/-0.05	
LMK212ABJ106 GHT				X5R	10 μ	±10, ±20	10	150	1.25+0.15/-0.05	
JMK212ABJ475[]GHT				X5R	4.7 μ	±10, ±20	5	200	1.25+0.15/-0.05	
JMK212ABJ106[]GHT		6.3		X5R	10 μ	±10, ±20	10	150	1.25+0.15/-0.05	
JMK212BBJ226MGHT				X5R	22 μ	±20	10	150	1.25+0.20/-0	
AMK212ABJ226MGHT		4		X5R	22 μ	±20	10	150	1.25+0.15/-0.05	
AMK212BBJ476MGHT		4		X5R	47 μ	±20	10	150	1.25+0.20/-0	

[Temperature Characteristic BJ : $X5R(-55 \sim +85^{\circ}C)$] 0.85mm thickness(D)

Part number 1	Part number 2	Rated voltage [V]	Temper characte		Capacitance [F]	Capacitance tolerance [%]	tan δ [%]	HTLT Rated voltage x %	Thickness*1 [mm]	Note
EMK212 BJ105 DHT				X5R	1 μ	±10, ±20	5	200	0.85±0.10	
EMK212ABJ225[]DHT		16		X5R	2.2 μ	±10, ±20	5	150	0.85±0.10	
EMK212BBJ475 DHT				X5R	4.7 μ	±10, ±20	10	150	0.85±0.10	

[Temperature Characteristic B7 : X7R(-55~+125°C)] 1.25mm thickness(G)

Part number 1	Part number 2	Rated voltage [V]	Temper characte		Capacitance [F]	Capacitance tolerance [%]	tan δ [%]	HTLT Rated voltage x %	Thickness*1 [mm]	Note
JMK212 B7103∏GHT				X7R	0.01 μ	±10, ±20	3.5	200	1.25±0.10	
JMK212 B7153∏GHT				X7R	0.015 μ	±10, ±20	2.5	200	1.25±0.10	
JMK212 B7223∏GHT				X7R	0.022 μ	±10, ±20	3.5	200	1.25±0.10	
IMK212 B7333∏GHT				X7R	0.033 μ	±10, ±20	3.5	200	1.25±0.10	
IMK212 B7473∏GHT				X7R	0.047 μ	±10, ±20	3.5	200	1.25±0.10	
MK212 B7683 GHT				X7R	0.068 μ	±10, ±20	3.5	200	1.25±0.10	
MK212 B7104[]GHT		50		X7R	0.1 μ	±10, ±20	3.5	200	1.25±0.10	
MK212BB7154 GHTE]		X7R	0.15 μ	±10, ±20	3.5	200	1.25+0.2/-0	
MK212 B7224[]GHT				X7R	0.22 μ	±10, ±20	3.5	150	1.25±0.10	
MK212BC7334[]GHTE				X7S	0.33 μ	±10, ±20	3.5	150	1.25+0.2/-0	
MK212 C7474[GHTE				X7S	0.47 μ	±10, ±20	3.5	150	1.25±0.10	
MK212CC7684∏GHTE				X7S	0.68 μ	±10, ±20	3.5	150	1.25+0.25/-0	
MK212 B7105[]GHT				X7R	1 μ	±10, ±20	10	150	1.25±0.10	
MK212 B7224[]GHT		35		X7R	0.22 μ	±10, ±20	3.5	150	1.25±0.10	
MK212 B7105 GHT		35		X7R	1 μ	±10, ±20	10	150	1.25±0.10	
MK212 B7224[]GHT				X7R	0.22 μ	±10, ±20	3.5	150	1.25±0.10	
MK212 B7334[]GHT				X7R	0.33 μ	±10, ±20	3.5	200	1.25±0.10	
MK212 B7474[]GHT		25		X7R	0.47 μ	±10, ±20	3.5	150	1.25±0.10	
MK212 B7105[]GHTR				X7R	1 μ	±10, ±20	10	150	1.25±0.10	
MK212 B7225[]GHT				X7R	2.2 μ	±10, ±20	10	150	1.25±0.10	
MK212 B7224[]GHT				X7R	0.22 μ	±10, ±20	3.5	200	1.25±0.10	
MK212 B7334[]GHT				X7R	0.33 μ	±10, ±20	3.5	200	1.25±0.10	
MK212 B7474[]GHT		16		X7R	0.47 μ	±10, ±20	3.5	200	1.25±0.10	
MK212 B7105[]GHTR		10		X7R	1 μ	±10, ±20	10	150	1.25±0.10	
MK212 B7225[]GHT				X7R	2.2 μ	±10, ±20	10	150	1.25±0.10	
MK212AB7475[]GHT		1		X7R	4.7 μ	±10, ±20	10	150	1.25+0.15/-0.05	
MK212 B7105[]GHTR				X7R	1 μ	±10, ±20	10	150	1.25±0.10	
MK212 B7225∏GHT		10		X7R	2.2 μ	±10, ±20	10	150	1.25±0.10	
MK212 B7475[]GHT		1		X7R	4.7 μ	±10, ±20	10	150	1.25±0.10	
MK212 B7475[]GHT		6.2		X7R	4.7 μ	±10, ±20	10	150	1.25±0.10	
MK212AB7106∏GHT		6.3		X7R	10 μ	±10, ±20	10	150	1.25+0.15/-0.05	

[▶] This catalog contains the typical specification only due to the limitation of space. When you consider the purchase of our products, please check our product specification sheets. For details of each product (characteristics graph, reliability information, precautions for use, and so on), see our website (http://www.ty-top.com/).

■316TYPE (Dimension:3.2 × 1.6mm JIS:3216 EIA:1206)

[Temperature Characteristic BJ : $X5R(-55 \sim +85^{\circ}C)$] 1.6mm thickness(L)

Part number 1	Part number 2	Rated voltage	Tempe	rature	Capacitance	Capacitance	tan δ	HTLT	*1 []	Note
Part number 1	Part number 2	[V]	characte	eristics	[F]	tolerance [%]	[%]	Rated voltage x %	Thickness*1 [mm]	Note
UMK316 BJ474□LHT				X5R	0.47 μ	±10, ±20	3.5	200	1.6±0.20	
UMK316 BJ105□LHT		50		X5R	1 μ	±10, ±20	3.5	200	1.6±0.20	
UMK316 BJ225□LHT		30		X5R	2.2 μ	±10, ±20	10	150	1.6±0.20	
UMK316ABJ475□LHT				X5R	4.7 μ	±10, ±20	10	150	1.6±0.20	
GMK316 BJ105□LHT				X5R	1 μ	$\pm 10, \pm 20$	3.5	200	1.6±0.20	
GMK316 BJ225□LHT		35		X5R	2.2 μ	$\pm 10, \pm 20$	10	150	1.6±0.20	
GMK316 BJ475□LHT		33		X5R	4.7 μ	±10, ±20	10	150	1.6±0.20	
GMK316BBJ106□LHT				X5R	10 μ	±10, ±20	10	150	1.6±0.30	
TMK316 BJ225 LHT				X5R	2.2 μ	±10, ±20	3.5	200	1.6±0.20	
TMK316 BJ475 LHT		25		X5R	4.7 μ	±10, ±20	5	150	1.6±0.20	
TMK316 BJ106□LHT				X5R	10 μ	±10, ±20	5	150	1.6±0.20	
EMK316 BJ225 LHT				X5R	2.2 μ	±10, ±20	3.5	200	1.6±0.20	
EMK316 BJ475 LHT		16		X5R	4.7 μ	±10, ±20	5	150	1.6±0.20	
EMK316 BJ106 LHT		10		X5R	10 μ	±10, ±20	5	150	1.6±0.20	
EMK316BBJ226MLHT				X5R	22 μ	±20	10	150	1.6±0.30	
LMK316 BJ475[LHT				X5R	4.7 μ	±10, ±20	5	150	1.6±0.20	
LMK316 BJ106[]LHT		10		X5R	10 μ	±10, ±20	5	150	1.6±0.20	
LMK316ABJ226 LHT				X5R	22 μ	±10, ±20	10	150	1.6±0.20	
JMK316 BJ106[]LHT				X5R	10 μ	±10, ±20	5	200	1.6±0.20	
JMK316ABJ226 LHT		6.3		X5R	22 μ	±10, ±20	10	150	1.6±0.20	
JMK316ABJ476MLHT				X5R	47 μ	±20	10	150	1.6±0.20	

Temperature Charac	teristic b7 . X/IV(123 (5), 67.7	×/3(-	33.5 + 123 C/J	1.6mm thicknes	1			
Part number 1	Part number 2	Rated voltage	Temper		Capacitance	Capacitance	tan δ	HTLT	Thickness*1 [mm]	Note
T di c Hambor T	T di C Hallibor E	[V]	characte	eristics	[F]	tolerance [%]	[%]	Rated voltage x %	THIORIESS EITING	
UMK316 B7473∏LHT				X7R	0.047 μ	±10, ±20	3.5	200	1.6±0.20	
UMK316 B7683∏LHT				X7R	0.068 μ	±10, ±20	2.5	200	1.6 ± 0.20	
JMK316 B7104□LHT				X7R	0.1 μ	±10, ±20	3.5	200	1.6 ± 0.20	
JMK316 B7154□LHT				X7R	0.15 μ	±10, ±20	3.5	200	1.6±0.20	
JMK316 B7224□LHT				X7R	0.22 μ	±10, ±20	3.5	200	1.6±0.20	
JMK316 B7334[]LHT		50		X7R	0.33 μ	±10, ±20	3.5	200	1.6±0.20	
JMK316 B7474[]LHT				X7R	0.47 μ	±10, ±20	3.5	200	1.6±0.20	
JMK316 B7105[]LHT				X7R	1 μ	±10, ±20	3.5	200	1.6±0.20	
IMK316BC7155□LHTE				X7S	1.5 μ	±10, ±20	3.5	150	1.6±0.30	
JMK316 B7225[]LHT				X7R	2.2 μ	±10, ±20	10	150	1.6±0.20	
MK316AC7475□LHTE				X7S	4.7 μ	±10, ±20	2.5	150	1.6±0.20	
MK316 B7105[]LHT				X7R	1 μ	±10, ±20	3.5	200	1.6±0.20	
MK316 B7225 LHT		35		X7R	2.2 μ	±10, ±20	10	150	1.6±0.20	
MK316AB7475[]LHT				X7R	4.7 μ	±10, ±20	10	150	1.6±0.20	
MK316 B7105[]LHT				X7R	1 μ	±10, ±20	3.5	200	1.6±0.20	
MK316 B7225 LHT		25		X7R	2.2 μ	±10, ±20	3.5	200	1.6±0.20	
MK316AB7475 LHT		25		X7R	4.7 μ	±10, ±20	10	150	1.6±0.20	
MK316AB7106 LHT				X7R	10 μ	±10, ±20	10	150	1.6±0.20	
MK316 B7225 LHT				X7R	2.2 μ	±10, ±20	3.5	200	1.6±0.20	
MK316AB7475[]LHT	•	16		X7R	4.7 μ	±10, ±20	10	150	1.6±0.20	
MK316AB7106[]LHT	•			X7R	10 μ	±10, ±20	10	150	1.6±0.20	
MK316 B7475 LHT	•	10		X7R	4.7 μ	±10, ±20	5	150	1.6±0.20	
MK316AB7106[]LHT	•	10		X7R	10 μ	±10, ±20	10	150	1.6±0.20	
MK316AB7106[]LHT		6.3		X7R	10 μ	±10, ±20	10	150	1.6±0.20	
IMK316AB7226∏LHT		0.3		X7R	22 μ	±10, ±20	10	150	1.6±0.20	
AMK316AB7226[]LHT		4		X7R	22 μ	±10, ±20	10	150	1.6±0.20	
AMK316AC7476MLHT		1 4		X7S	47 μ	±20	10	150	1.6±0.20	

16

[▶] This catalog contains the typical specification only due to the limitation of space. When you consider the purchase of our products, please check our product specification sheets. For details of each product (characteristics graph, reliability information, precautions for use, and so on), see our website (http://www.ty-top.com/).

325TYPE (Dimension:3.2 × 2.5mm JIS:3225 EIA:1210)

[Temperature Characteristic BJ : $X5R(-55 \sim +85^{\circ}C)$] 2.5mm thickness(M)

Part number 1	Part number 2	Rated voltage	Tempe	erature	Capacitance	Capacitance	tan δ	HTLT	Thickness*1 [mm]	Note
Part number 1	Part number 2	[V]	charact	eristics	[F]	tolerance [%]	[%]	Rated voltage x %	Inickness [mm]	Note
UMK325 BJ106□MHP		50		X5R	10 μ	±10, ±20	5	150	2.5±0.20	
GMK325 BJ106□MHP		35		X5R	10 μ	±10, ±20	5	150	2.5±0.20	
TMK325 BJ106□MHP		25		X5R	10 μ	±10, ±20	5	150	2.5±0.20	
EMK325 BJ226 MHP		16		X5R	22 μ	±10, ±20	5	150	2.5±0.20	
EMK325ABJ476□MHP		10		X5R	47 μ	±10, ±20	10	150	2.5±0.30	
LMK325 BJ226 MHP		10		X5R	22 μ	±10, ±20	5	150	2.5±0.20	
LMK325 BJ476∏MHP		10		X5R	47 μ	±10, ±20	10	150	2.5±0.20	
JMK325 BJ476∏MHP		6.3		X5R	47 μ	±10, ±20	10	150	2.5±0.20	

[Temperature Characteristic BJ : $X5R(-55 \sim +85^{\circ}C)$] 1.9mm thickness(N)

Part number 1	Part number 2	Rated voltage [V]	erature eristics	Capacitance [F]	Capacitance tolerance [%]	tan δ [%]	HTLT Rated voltage x %	Thickness*1 [mm]	Note
UMK325 BJ475[NHT		50	X5R	4.7 μ	±10, ±20	10	150	1.9±0.20	
GMK325 BJ225MNHT		35	X5R	2.2 μ	±20	3.5	200	1.9±0.20	
GMK325 BJ475∏NHT		30	X5R	4.7 μ	±10, ±20	10	150	1.9±0.20	
TMK325 BJ475□NHT		25	X5R	4.7 μ	±10, ±20	10	150	1.9±0.20	
EMK325 BJ475MNHT		16	X5R	4.7 μ	±20	3.5	200	1.9±0.20	
EMK325 BJ106□NHT		10	X5R	10 μ	±10, ±20	5	150	1.9±0.20	

[Temperature Characteristic B7 : X7R($-55\sim+125^{\circ}$ C)] 2.5mm thickness(M)

Part number 1	Part number 2	Rated voltage	Temperatur	е	Capacitance	Capacitance	tan δ	HTLT	Thickness*1 [mm]	N. s.
Part number I	Part number 2	[V]	characteristi	cs	[F]	tolerance [%]	[%]	Rated voltage x %	Thickness [mm]	Note
UMK325 B7225∏MHP			X7	'R	2.2 μ	±10, ±20	3.5	200	2.5±0.20	
UMK325 B7335∏MHP		50	X7	'R	3.3 μ	±10, ±20	3.5	200	2.5±0.20	<u>.</u>
UMK325 B7475∏MHP		50	X7	′R	4.7 μ	±10, ±20	5	150	2.5±0.20	
UMK325AB7106□MHP			X7	7R	10 μ	±10, ±20	10	150	2.5±0.30	
GMK325AB7106[]MHP		35	X7	7R	10 μ	±10, ±20	10	150	2.5±0.30	
TMK325 B7335 MHP			X7	7R	3.3 μ	±10, ±20	3.5	200	2.5±0.20	
TMK325AB7106□MHPR		25	X7	′R	10 μ	±10, ±20	10	150	2.5±0.30	
TMK325 B7226 MHP			X7	′R	22 μ	±10, ±20	10	150	2.5±0.20	
EMK325 B7226 MHP		16	X7	7R	22 μ	$\pm 10, \pm 20$	10	150	2.5±0.20	
LMK325 B7226 MHP		10	X7	7R	22 μ	$\pm 10, \pm 20$	10	150	2.5±0.20	
JMK325 B7226 ☐ MHPR		6.3	X7	′R	22 μ	±10, ±20	10	150	2.5±0.20	
JMK325 B7476 MHPR		0.5	X	'R	47 μ	±10, ±20	10	150	2.5±0.20	

[Temperature Characteristic B7 : X7R($-55\sim+125^{\circ}$ C)] 1.9mm thickness(N)

Part number 1	Part number 2	Rated voltage [V]	rature eristics	Capacitance [F]	Capacitance tolerance [%]	tan δ [%]	HTLT Rated voltage x %	Thickness*1 [mm]	Note
UMK325 B7105∏NHT		50	X7R	1 μ	±10, ±20	3.5	200	1.9±0.20	
GMK325 B7225 NHT		35	X7R	2.2 μ	±10, ±20	3.5	200	1.9±0.20	
GMK325 B7475 NHTR		33	X7R	4.7 μ	±10, ±20	10	150	1.9±0.20	
TMK325 B7475[]NHT		25	X7R	4.7 μ	±10, ±20	10	150	1.9±0.20	
EMK325 B7475 NHT		16	X7R	4.7 μ	±10, ±20	3.5	150	1.9±0.20	
EMK325 B7106 NHTR		10	X7R	10 μ	±10, ±20	10	150	1.9±0.20	

[▶] This catalog contains the typical specification only due to the limitation of space. When you consider the purchase of our products, please check our product specification sheets. For details of each product (characteristics graph, reliability information, precautions for use, and so on), see our website (http://www.ty-top.com/).

Multilayer Ceramic Capacitors

■PACKAGING

1)Minimum Quantity


T (514)	Thick	ness	Standard of	quantity [pcs]
Type(EIA)	mm	code	Paper tape	Embossed tape
□MK021(008004)	0.105	V		F0000
□VS021(008004)	0.125	К	_	50000
☐MK042(01005)	0.2	C, D		40000
□VS042(01005)	0.2	С		40000
☐MK063(0201)	0.3	P,T	15000	_
□WK105(0204) ※	0.3	Р	10000	_
	0.13	Н	_	20000
Thu(105(0400)	0.18	E	_	15000
☐MK105(0402)	0.2	С	20000	_
□MF105(0402)	0.3	Р	15000	_
	0.5	٧	10000	_
□VK105(0402)	0.5	W	10000	_
□MK107(0603)	0.45	K	4000	_
□WK107(0306) ※	0.5	V	_	4000
□MF107(0603)	0.8	Α	4000	_
□VS107(0603)	0.7	С	4000	_
□MJ107(0603)	0.8	Α	3000	3000
□MK212(0805)	0.45	K	4000	
□WK212(0508) ※	0.85	D	4000	_
□MF212(0805)	1.25	G	_	3000
□VS212(0805)	0.85	D	4000	_
[] N. 104.0(0.005)	0.85	D	4000	_
□MJ212(0805)	1.25	G	_	2000
DM (040(4000)	0.85	D	4000	_
☐MK316(1206)	1.15	F	_	3000
□MF316(1206)	1.6	L	_	2000
The 1040(4000)	1.15	F	_	3000
□MJ316(1206)	1.6	L	_	2000
	0.85	D		
DM/205(1010)	1.15	F		2000
□MK325(1210)	1.9	N		2000
]MF325(1210)	2.0max.	Υ		
	2.5	М	_	1000
MJ325(1210)	1.9	N	_	2000
□INIO9520(1510)	2.5	М	_	500(T), 1000(P)
□MK432(1812)	2.5	М	_	500

Note:


K LW Reverse type.

**No bottom tape for pressed carrier tape Card board carrier tape Top tape Base tape Sprocket hole Chip cavity Base tape Chip cavity

This catalog contains the typical specification only due to the limitation of space. When you consider the purchase of our products, please check our specification. For details of each product (characteristics graph, reliability information, precautions for use, and so on), see our Web site (http://www.ty-top.com/).




3 Representative taping dimensions




Type(EIA)	Chip	Cavity	Insertion Pitch	Tape Th	nickness
Type(EIA)	Α	В	F	Т	T1
□MK063(0201)	0.37	0.67		0.45max.	0.42max.
□WK105(0204) ※			2.0±0.05	0.45max.	0.42max.
□MK105(0402) (*1 C)	0.65	1.15	2.0±0.05	0.4max.	0.3max.
□MK105(0402) (*1 P)				0.45max.	0.42max.

Note *1 Thickness, C:0.2mm ,P:0.3mm. * LW Reverse type.

Unit:mm



Type(EIA)	Chip	Cavity	Insertion Pitch	Tape Thickness
Type(EIA)	Α	В	F	Т
☐MK105 (0402)				
☐MF105 (0402)	0.65	1.15	2.0 ± 0.05	0.8max.
□VK105 (0402)				
	•			Unit:mm




This catalog contains the typical specification only due to the limitation of space. When you consider the purchase of our products, please check our specification. For details of each product (characteristics graph, reliability information, precautions for use, and so on), see our Web site (http://www.ty-top.com/).

Type(EIA)	Chip (Cavity	Insertion Pitch	Tape Thickness
Type(EIA)	Α	В	F	Т
☐MK107(0603)				
□WK107(0306) ※	1.0	1.8		1.1max.
☐MF107(0603)			40+01	
☐MK212(0805)	1.65	0.4	4.0±0.1	
□WK212(0508) ※	1.65	2.4		1.1max.
☐MK316(1206)	2.0	3.6		


Note: Taping size might be different depending on the size of the product. X LW Reverse type.

Unit:mm



Type(EIA)	Chip (Cavity	Insertion Pitch	Tape Ti	nickness
Type(EIA)	Α	В	F	K	Т
☐MK021(008004)	0.135	0.27			
□VS021(008004)	0.135	0.27	1.0±0.02	0.5max.	0.25max.
☐MK042(01005)	0.23	0.43	1.0 ± 0.02	o.omax.	0.25max.
□VS042(01005)	0.23	0.43			


Unit:mm



Type(EIA)	Chip (Cavity	Insertion Pitch	Tape Thickness		
Type(EIA)	Α	В	F	K	Т	
☐MK105(0402)	0.6	1.1	2.0±0.1	0.6max	0.2±0.1	
□WK107(0306) ※	1.0	1.8		1.3max.	0.25±0.1	
☐MK212(0805) ☐MF212(0805)	1.65	2.4				
☐MK316(1206) ☐MF316(1206)	2.0	3.6	4.0±0.1	3.4max.	0.6max.	
☐MK325(1210) ☐MF325(1210)	2.8	3.6]			

Note: ※ LW Reverse type. Unit:mm


This catalog contains the typical specification only due to the limitation of space. When you consider the purchase of our products, please check our specification. For details of each product (characteristics graph, reliability information, precautions for use, and so on), see our Web site (http://www.ty-top.com/).




Type(EIA)	Chip (Cavity	Insertion Pitch	Tape Thickness		
Type(EIA)	Α	В	F	K	Т	
☐MK325(1210)	3.1 4.0		8.0±0.1	4.0max.	0.6max.	
☐MK432(1812)	3.7	4.9	8.0±0.1	4.0max.	0.6max.	

Unit:mm

4 Trailer and Leader



⑤Reel size




Α	В	С	D	E	R
ϕ 178 ± 2.0	<i>ф</i> 50min.	ϕ 13.0 \pm 0.2	ϕ 21.0 ± 0.8	2.0±0.5	1.0

	T	W
4mm wide tape	1.5max.	5±1.0
8mm wide tape	2.5max.	10±1.5
12mm wide tape	2.5max.	14±1.5

Unit:mm

6Top Tape Strength

The top tape requires a peel-off force of 0.1 to 0.7N in the direction of the arrow as illustrated below.



This catalog contains the typical specification only due to the limitation of space. When you consider the purchase of our products, please check our specification. For details of each product (characteristics graph, reliability information, precautions for use, and so on), see our Web site (http://www.ty-top.com/).

Multilayer Ceramic Capacitors

■RELIABILITY DATA

Specified

1.Operating To	emperature Range								
	Temperature Standard		FF 1 140F ⁰ O						
	Compensating(Class1)	High Frequency Type	-55 to 7	−55 to +125°C					
				Specification	Temperature Range				
			BJ	В	−25 to +85°C				
Specified			ВО	X5R	−55 to +85°C				
Value					−55 to +125°C				
	High Permittivity (Class2)	C6	X6S	−55 to +105°C					
		C7	X7S	−55 to +125°C					
		D7	X7T	−55 to +125°C					
		LD(※)	X5R	−55 to +85°C					
					high value multilayer ceramic capa	citor			
2. Storage Co	nditions								
	Temperature Standard Compensating(Class1) High Frequency Type		−55 to +	L 125°C					
			_33 to T	- 123 C					
				Specification	Temperature Range				
			R I	В	−25 to +85°C				

Value		B7	X7R	−55 to +125°C
	High Permittivity (Class2)	C6	X6S	−55 to +105°C
		C7	X7S	−55 to +125°C
		D7	X7T	−55 to +125°C
		LD(※)	X5R	−55 to +85°C
		Moto: V	ID Law distartion	high value multilever ecremie ecne

В7

Note: XLD Low distortion high value multilayer ceramic capacitor

-55 to +85°C

-55 to +125°C

3. Rated Voltage								
	Temperature	Standard	50VDC, 25VDC					
Specified Value	Compensating(Class1)	High Frequency Type	50VDC, 25VDC					
value	High Permittivity (Class2))	50VDC, 35VDC, 25VDC, 16VDC, 10VDC, 6.3VDC, 4VDC, 2.5VDC					

X5R

X7R

4. Withstanding	Voltage (Between terminal	s)					
Specified Value	Temperature	Standard					
	Compensating(Class1)	High Frequency T	ype No breakdown	No breakdown or damage			
	High Permittivity (Class2))					
- .			Class 1	Class 2			
Test Methods and	Applied voltage	Applied voltage Rated		Rated voltage × 2.5			
Remarks	Duration		1 to	5 sec.			
	Charge/discharge current		50m.	A max.			

5. Insulation Re	5. Insulation Resistance						
·	Temperature	Standard	10000 MΩ min.				
	Compensating(Class1)	High Frequency Type	TOUGO M SZ MIIN.				
Value	High Permittivity (Class2)	Note 1	C ≤ 0.047 μ F : 10000 M Ω min. C > 0.047 μ F : 500M Ω • μ F				
Test	Applied voltage	: Rated voltage					
Methods and	Duration	: 60±5 sec.					
Remarks	Charge/discharge current	: 50mA max.					

Finis catalog contains the typical specification only due to the limitation of space. When you consider the purchase of our products, please check our specification. For details of each product (characteristics graph, reliability information, precautions for use, and so on), see our Web site (http://www.ty-top.com/) .

6. Capacitance	(Tolerance)						
	Temperature	Standard High Frequency Type		C □ U □ SL	0.2pF≦C≦5pF 0.2pF≦C≦10pF C>10pF	: ±0.25pF : ±0.5pF : ±5% or ±10%	
Specified Value				СН	0.3pF≦C≦2pF C>2pF	: ±0.1pF : ±5%	
	High Permittivity (Class2)				7, C6, C7, D7, LD(※): ± ※LD Low distortion hig	±10% or ±20% h value multilayer ceramic	c capacitor
				Clas	ss 1	Cla	ass 2
- .		Standar		ł	High Frequency Type	C≦10 μ F	C>10 μ F
Test	Preconditioning			None		Thermal treatment (a	t 150°C for 1hr) Note 2
Methods and	Measuring frequency			1MHz	±10%	1kHz±10%	120±10Hz
Remarks	Measuring voltage Note		0.5 to 5Vrms			1±0.2Vrms	0.5±0.1rms
	Bias application					None	•

Specified Value	Temperature		Standard $C < 30pF : Q \ge 400 + 20C$ $C \ge 30pF : Q \ge 1000$ (C:Nom			ominal capacitance)		
	Compensating(Class1)	High F	requency Type	Refer	to detailed specification			
	High Permittivity (Class2) Note 1			BJ, B	7, C6, C7, D7:2.5% max.			
				Class 1		Clas	ss 2	
			Standard		High Frequency Type	C≦10 μ F	C>10 μ F	
	Preconditioning			None		Thermal treatment (at	150°C for 1hr) Note 2	
Test	Measuring frequey		1MHz±10%		1GHz	1kHz±10%	120±10Hz	
Methods and	Measuring voltage Note 1		0.5 to 5Vrms 1±0.2Vrms 0.5±0.1Vrms					
Remarks	Bias application			None				
	High Frequency Type							
	Measuring equipment	: HP	4291A					
	Measuring jig : HP16192A							

			Temperature Characteristic [ppm/°C]			C]	Tolerance [ppm/°C]	
			C□:	0	CG,CH, CJ,	СК	G: ±30 H: ±60	
	Temperature Compensating(Class1)	Standard	U□ :	— 750	UJ, UK		J : ±120 K : ±250	
	Componenting (Classify		SL :	+350 to −100	00			
		High Eraguanay Typa	Tem	perature Charac	cteristic [ppm/°	C]	Toler	ance [ppm/°C]
Specified Value		High Frequency Type	C□:	0	CH			H: ±60
			Specification	Capacitance change	Refere tempera		Temperature Range	
		BJ	В	±10%	20°0	С	−25 to +85°C	
		БО	X5R	±15%	25°0	С	−55 to +85°C	
	High Dormittivity (Close?)	B7	X7R	±15%	25°0	С	-55 to +125°C	
	High Permittivity (Glassz)	High Permittivity (Class2)			±22%	25°0	С	-55 to +105°C
					±22%	25°0	0	-55 to +125°C
					+22/-33%	25°0	С	-55 to +125°C
					±15%	25°0	С	−55 to +85°C
		Note:		ortion high value				

Class 1: Capacitance at 20°C and 85°C shall be measured in thermal equilibrium, and the temperature characteristic shall be calculated from the following equation.

$$\frac{(C_{85}-C_{20})}{C_{20}\times\Delta T} \times 10^{6} (ppm/^{\circ}C) \qquad \Delta T = 65$$

Class 2: Capacitance at each step shall be measured in thermal equilibrium, and the temperature characteristic shall be calculated from the

lest	Tollowing equation	ori.			
Methods and	Step	В	X5R, X7R, X6S, X7S		
Remarks	1	Minimum operating temperature			
	2	20°C	25°C		
	3	Maximum operat	ing temperature		

× 100 (%) C₂

Test

: Capacitance in Step 1 or Step 3

C2 : Capacitance in Step 2

Finis catalog contains the typical specification only due to the limitation of space. When you consider the purchase of our products, please check our specification. For details of each product (characteristics graph, reliability information, precautions for use, and so on), see our Web site (http://www.ty-top.com/) .

9. Deflection						
Specified Value	Temperature	Standard	Appearance Capacitance change	: No abnormality : Within $\pm 5\%$ or ± 0.5 pF, whichever is larger.		
	Compensating (Cl	High Frequency Type	Appearance Cpaitance change	: No abnormality : Within±0.5 pF		
Value	High Permittivity	Appearance Capacitance	Capacitance change	nce : No abnormality nnce change : Within ±12.5%(BJ, B7, C6, C7, D7, LD(※)) (LD Low distortion high value multilayer ceramic capacitor		
		Multilayer Cerar	nic Capacitors	20,		
		042, 063, ^{※1} 105 Type	The other types	Board R-230 Warp		
Test	Board	Glass epoxy-re	sin substrate			
Methods and	Thickness	0.8mm	1.6mm	45±2 45±2 1		
Remarks	Warp	1mm (Soft Termin	nation type:3mm)	1022 (1022		
	Duration	10 s	ec.	(Unit: mm)		
		*1:105 Type thickness, C: 0.	2mm ,P: 0.3mm.	Capacitance measurement shall be conducted with the board bent		

	Temperature	Standard	-
Specified Value	Compensating(Class1)	High Frequency Type	No mechanical damage.
Value	High Permittivity (Class2))	_
Test Methods and Remarks	High Frequency Type Applied force : 5N Duration : 10 sec.	Pres ← A →	R0.5 Pressing jig Chip Chip

11. Adhesive St	11. Adhesive Strength of Terminal Electrodes						
0 '5 1	Temperature	Standard		No terminal separation or its indication.			
Specified Value	Compensating(Class1)	High Frequency Typ	e No terminal separati				
Value	High Permittivity (Cla	ss2)					
T4		Multilayer Cerar	nic Capacitors				
Test Methods and		042, 063 Type	105 Type or more				
Remarks	Applied force	2N	5N				
i (ciliai KS	Duration	30±5	sec.				

12. Solderability	/		_		
0 :5 1	Temperature	Standard			
Specified Value	Compensating(Class1)	High Frequency Type	At least 95% of terminal electrode is covered by		by new solder.
value	High Permittivity (Class2))			
- .	Eutectic s		older	Lead-free solder	
Test Methods and	Solder type	H60A or H	63A	Sn-3.0Ag-0.5Cu	
Remarks	Solder temperature	230±5°	С	245±3°C	
	Duration		4±1 sec.		

This catalog contains the typical specification only due to the limitation of space. When you consider the purchase of our products, please check our specification. For details of each product (characteristics graph, reliability information, precautions for use, and so on), see our Web site (http://www.ty-top.com/).

13. Resistance	to Soldering				
Specified Value	Temperature	Standard	Appearance Capacitance change Q Insulation resistance Withstanding voltage	: No abnormality : Within ±2.5% or ±0. : Initial value : Initial value (between terminals)	25pF, whichever is larger. : No abnormality
	Compensating(Class1)	High Frequency Type	Appearance Capacitancecange Q Insulation resistance Withstanding voltage	: No abnormality : Within ±2.5% : Initial value : Initial value (between terminals): No abnormality	
	High Permittivity (Class2) Note 1		Appearance Capactace change Dissipation factor Insulation resistance Withstanding voltage Note: ※LD Low distort	: No abormality : Within ±7.5%(BJ, B7 : Initial value : Initial value (between terminals): l tion high value multilayer	No abnormality
		Class 1			
		042, 063 Type	105 Туре		
	Preconditioning		None		
	Preheating	150°C, 1 to 2 min.		0°C, 2 to 5 min. 00°C, 2 to 5 min.	
	Solder temp.		270±5°C		
	Duration		3±0.5 sec.		
est	Recovery	6 to 24 hrs	s(Standard condition)N	loe 5	
Methods and					
Remarks	_			Class 2	
		042,063 Type		07, 212 Type	316, 325 Type
	Preconditioning			(at 150°C for 1 hr) Not	
	Preheating	150°C, 1 to 2 min.		0°C, 2 to 5 min. 00°C, 2 to 5 min.	80 to 100°C, 5 to 10 min. 150 to 200°C, 5 to 10 min.
	Solder temp.		2	70±5℃	
	Duration		3:	±0.5 sec.	
	Recovery		24±2 hrs(Stan	dard condition) Note 5	

14. Temperatur	re Cycle (Thermal Shock)						
Specified Value	Temperature	Standard		Appearance Capacitance change Q Insulation resistance Withstanding voltage	: No abnormality : Within ±2.5% or ±0.25 : Initial value : Initial value (between terminals) : N	•	
	Compensating(Class1)	High Frequency Type		Appearance Capacitance change Q Insulation resistance Withstanding voltage	: Initial value ance : Initial value		
	High Permittivity(Class2) Note 1			Appearance : No abnormality Capacitance change : Within ±7.5% (BJ, B7, C6, C7, D7, LD(※)) Dissipation factor : Initial value Insulation resistance : Initial value Withstanding voltage (between terminals) : No abnormality Note: ※LD Low distortion high value multilayer ceramic capacitor			
			C	Class 1		Class 2	
	Preconditioning	None			Thermal trea	tment (at 150°C for 1 hr) Note 2	
Test Methods and Remarks	1 cycle	Step Temperature 1 Minimum operating to Normal tempet and Maximum operating to Normal tempet tempet to Normal tempet te			ting temperature 30 ± 3 mperature 2 to 3 ming temperature 30 ± 3		
	Number of cycles				5 times		
	Recovery	6 to 24 hrs	s (Stan	dard condition)Note 5	24±2 hrs (5	Standard condition)Note 5	

This catalog contains the typical specification only due to the limitation of space. When you consider the purchase of our products, please check our specification. For details of each product (characteristics graph, reliability information, precautions for use, and so on), see our Web site (http://www.ty-top.com/).

15. Humidity (Steady State)						
	Temperature Compensating(Class1	Standard	Standard Capacitance change : W Q : C		bnormality $n \pm 5\% \text{ or } \pm 0.5 \text{pF, whichever is larger.}$ $0 \text{pF}: Q \geqq 200 + 10 \text{C}$ $\leqq C < 30 \text{pF}: Q \leqq 275 + 2.5 \text{C}$ $30 \text{pF}: Q \leqq 350 (C: \text{Nominal capacitance})$ $M \Omega \text{ min.}$		
Specified Value		High Frequency Type	Appearance Capacitance change Insulation resistance	: Withi	: No abnormality : Within $\pm 0.5 \text{pF}$, : 1000 M Ω min.		
	High Permittivity(Class2) Note 1		Appearance Capacitance change Dissipation factor Insulation resistance Note: **LD Low distort	Capacitance change : Within ±12.5% (BJ, B7, C6, C7, D7, LD(**)) Dissipation factor : 5.0% max.(BJ, B7, C6, C7, D7, LD(**))			
			ass 1		Class 2		
_	D 191	Standard	High Frequency Typ	е	All items		
Test Methods and	Preconditioning	40±2°C	one 60 ± 2°C		Thermal treatment(at 150°C for 1 hr) Note 2 40+2°C		
Remarks	Temperature Humidity		00±2℃ - 95%RH		90 to 95%RH		
i tomants	Duration		4/ —0 hrs		500+24/-0 hrs		
	Recovery		ard condition) Note 5		24±2 hrs (Standard condition) Note 5		

16. Humidity Lo	pading				
Specified Value	Temperature Compensating(Class1)	Standard	Appearance Capacitance change Q Insulation resistance	: No abnormality : Within $\pm 7.5\%$ or ± 0.75 pF, whichever is larger. : C <30 pF:Q $\ge 100+10$ C/3 C ≥ 30 pF:Q ≥ 200 (C:Nominal capacitance) : 500 M Ω min.	
	Compensating (Class 1)	High Frequency Type	$\begin{array}{lll} \mbox{Appearance} & : \mbox{No abnormality} \\ \mbox{Capacitance change} & : \mbox{C} \leq 2 \mbox{pF} : \mbox{Within } \pm 0.4 \mbox{ pF} \\ \mbox{C} > 2 \mbox{pF} : \mbox{Within } \pm 0.75 \mbox{ pF} \mbox{ (C} : \mbox{Nominal capacitance} \\ \mbox{Insulation resistance} & : 500 \mbox{ M} \mbox{min.} \end{array}$		
	High Permittivity (Class2) Note 1	Appearance : No abnormality Capacitance change : Within $\pm 12.5\%$ (BJ, B7, C6, C7, D7, LD($\%$)) Dissipation factor : 5.0% max. (BJ, B7, C6, C7, D7, LD($\%$)) Insulation resistance : 25 M Ω μ F or 500 M Ω , whichever is smaller. Note: $\%$ LD Low distortion high value multilayer ceramic capacitor		
		(Class 1	Class 2	
		Standard High Frequency Type		All items	
	Preconditioning		None	Voltage treatment (Rated voltage are applied for 1 hour at 40°C) Note 3	
Test	Temperature	$40\pm2^{\circ}C$	60±2°C	40±2°C	
Methods and	Humidity	90 1	to 95%RH	90 to 95%RH	
Remarks	Duration	500+	24/-0 hrs	500+24/-0 hrs	
	Applied voltage	Rate	ed voltage	Rated voltage	
	Charge/discharge current	50	mA max.	50mA max.	
	Recovery	6 to 24 hrs (Stan	dard condition)Note 5	24±2 hrs(Standard condition) Note 5	

17. High Temperature Loading

[►] This catalog contains the typical specification only due to the limitation of space. When you consider the purchase of our products, please check our specification. For details of each product (characteristics graph, reliability information, precautions for use, and so on), see our Web site (http://www.ty-top.com/).

	T		Ι.				
			Appearance	: No abnormality			
			Capacitance change	·			
		Standard	Q	: C<10pF: Q≧200+10C			
	Temperature			$10 \le C < 30pF: Q \ge 275 + 2.5C$			
	· · · · · · · · · · · · · · · · · · ·			C≧30pF: Q≧350(C:Nominal capacitance)			
	Compensating(Class1)		Insulation resistance	: 1000 M Ω min.			
Specified			Appearance	: No abnormality			
Value		High Frequency Type	Capacitance change	: Within $\pm 3\%$ or ± 0.3 pF, whichever is larger.			
			Insulation resistance	: 1000 MΩ min.			
			Appearance : No abnormality				
			Capacitance change	Capacitance change : Within ±12.5% (BJ, B7, C6, C7, D7, LD(※))			
	High Permittivity (Class2) Note 1	Dissipation factor	: 5.0% max.(BJ, B7, C6, C7, D7, LD(※))			
			Insulation resistance	Ξ : 50 MΩ μ F or 1000 MΩ, whichever is smaller.			
			Note: %LD Low dist	tortion high value multilayer ceramic capacitor			
		Clas	s 1	Class 2			
		Standard H	High Frequency Type	BJ, LD(<u>*</u>) C6 B7, C7, D7			
	D 1917 1	N		Voltage treatment (Twice the rated voltage shall be applied for			
	Preconditioning	Preconditioning Nor		1 hour at 85°C, 105°C or 125°C) Note 3, 4			
Test	Temperature	Maximum operati	ng temperature	Maximum operating temperature			
Methods and	Duration	1000+48	/-0 hrs	1000+48/-0 hrs			
Damarka	Applied voltage	Rated vol	tage × 2	Rated voltage × 2 Note 4			

Remarks

	C	Blass 1	Class 2			
	Standard	High Frequency Type	BJ, LD(※)	C6	B7, C7, D7	
Preconditioning		None	Voltage treatment (Twice the rated voltage shall be applied for 1 hour at 85°C, 105°C or 125°C) Note 3, 4			
Temperature	Maximum oper	rating temperature	Maximum operating temperature			
Duration	1000+	-48/-0 hrs	1000 + 48 / -0 hrs			
Applied voltage	Rated	voltage × 2	Rated voltage × 2 Note 4			
Charge/discharge current	50r	50mA max.		50mA max.		
Recovery	6 to 24hr (Stand	ard condition)Note 5	24±2 hrs(Standard condition)Note 5			

Note: XLD Low distortion high value multilayer ceramic capacitor

- Note 1 The figures indicate typical specifications. Please refer to individual specifications in detail.
- Note 2 Thermal treatment: Initial value shall be measured after test sample is heat-treated at 150+0/-10°C for an hour and kept at room temperature for 24 ± 2 hours.
- Note 3 Voltage treatment: Initial value shall be measured after test sample is voltage-treated for an hour at both the temperature and voltage specified in the test conditions, and kept at room temperature for 24 ± 2 hours.
- Note 4 150% of rated voltage is applicable to some items. Please refer to their specifications for further information.
- Note 5 Standard condition: Temperature: 5 to 35°C, Relative humidity: 45 to 85 % RH, Air pressure: 86 to 106kPa When there are questions concerning measurement results, in order to provide correlation data, the test shall be conducted under the following condition.
 - Temperature: 20±2°C, Relative humidity: 60 to 70 % RH, Air pressure: 86 to 106kPa Unless otherwise specified, all the tests are conducted under the "standard condition".

Finis catalog contains the typical specification only due to the limitation of space. When you consider the purchase of our products, please check our specification. For details of each product (characteristics graph, reliability information, precautions for use, and so on), see our Web site (http://www.ty-top.com/) .

Precautions on the use of Multilayer Ceramic Capacitors

■PRECAUTIONS

1. Circuit Design

- ◆ Verification of operating environment, electrical rating and performance
 - A malfunction of equipment in fields such as medical, aerospace, nuclear control, etc. may cause serious harm to human life or have severe social ramifications.

Therefore, any capacitors to be used in such equipment may require higher safety and reliability, and shall be clearly differentiated from them used in general purpose applications.

Precautions

- ◆Operating Voltage (Verification of Rated voltage)
 - 1. The operating voltage for capacitors must always be their rated voltage or less.
 - If an AC voltage is loaded on a DC voltage, the sum of the two peak voltages shall be the rated voltage or less.
 - For a circuit where an AC or a pulse voltage may be used, the sum of their peak voltages shall also be the rated voltage or less.
 - 2. Even if an applied voltage is the rated voltage or less reliability of capacitors may be deteriorated in case that either a high frequency AC voltage or a pulse voltage having rapid rise time is used in a circuit.

2. PCB Design

Precautions

- ◆Pattern configurations (Design of Land-patterns)
- 1. When capacitors are mounted on PCBs, the amount of solder used (size of fillet) can directly affect the capacitor performance. Therefore, the following items must be carefully considered in the design of land patterns:
 - (1) Excessive solder applied can cause mechanical stresses which lead to chip breaking or cracking. Therefore, please consider appropriate land-patterns for proper amount of solder.
 - (2) When more than one component are jointly soldered onto the same land, each component's soldering point shall be separated by solder-resist.
- ◆Pattern configurations (Capacitor layout on PCBs)

After capacitors are mounted on boards, they can be subjected to mechanical stresses in subsequent manufacturing processes (PCB cutting, board inspection, mounting of additional parts, assembly into the chassis, wave soldering of the boards, etc.). For this reason, land pattern configurations and positions of capacitors shall be carefully considered to minimize stresses.

◆Pattern configurations (Design of Land-patterns)


The following diagrams and tables show some examples of recommended land patterns to prevent excessive solder amounts.


- (1) Recommended land dimensions for typical chip capacitors
- Multilayer Ceramic Capacitors : Recommended land dimensions (unit: mm)

Wave-soldering

Type		107	107 212 316		325
Size	L	1.6	2.0	3.2	3.2
Size	W	0.8	1.25	1.6	2.5
A	4	0.8 to 1.0	1.0 to 1.4	1.8 to 2.5	1.8 to 2.5
В		0.5 to 0.8	0.8 to 1.5	0.8 to 1.7	0.8 to 1.7
С		0.6 to 0.8	0.9 to 1.2	1.2 to 1.6	1.8 to 2.5

Land patterns for PCBs





Technical considerations


Reflow-soldering

	Titeriow Soldering								
	Туре	042	063	105	107	212	316	325	432
Si	L	0.4	0.6	1.0	1.6	2.0	3.2	3.2	4.5
SI	W	0.2	0.3	0.5	0.8	1.25	1.6	2.5	3.2
	Α	0.15 to 0.25	0.20 to 0.30	0.45 to 0.55	0.8 to 1.0	0.8 to 1.2	1.8 to 2.5	1.8 to 2.5	2.5 to 3.5
	В	0.15 to 0.20	0.20 to 0.30	0.40 to 0.50	0.6 to 0.8	0.8 to 1.2	1.0 to 1.5	1.0 to 1.5	1.5 to 1.8
	С	0.15 to 0.30	0.25 to 0.40	0.45 to 0.55	0.6 to 0.8	0.9 to 1.6	1.2 to 2.0	1.8 to 3.2	2.3 to 3.5

 $Note: Recommended \ land \ size \ might \ be \ different \ according \ to \ the \ allowance \ of \ the \ size \ of \ the \ product.$


●LWDC: Recommended land dimensions for reflow-soldering (unit: mm)

Туре		105	107	212
Size	L	0.52	0.8	1.25
	W	1.0	1.6	2.0
Α		0.18 to 0.22	0.25 to 0.3	0.5 to 0.7
В		0.2 to 0.25	0.3 to 0.4	0.4 to 0.5
С		0.9 to 1.1	1.5 to 1.7	1.9 to 2.1



[▶] This catalog contains the typical specification only due to the limitation of space. When you consider the purchase of our products, please check our specification For details of each product (characteristics graph, reliability information, precautions for use, and so on), see our Web site (http://www.ty~top.com/).


(2) Examples of good and bad solder application



- ◆Pattern configurations (Capacitor layout on PCBs)
 - 1-1. The following is examples of good and bad capacitor layouts; capacitors shall be located to minimize any possible mechanical stresses from board warp or deflection.

Items	Not recommended	Recommended	
Deflection of board		Place the product at a right angle to the direction of the anticipated mechanical stress.	

1-2. The amount of mechanical stresses given will vary depending on capacitor layout. Please refer to diagram below.



1-3. When PCB is split, the amount of mechanical stress on the capacitors can vary according to the method used. The following methods are listed in order from least stressful to most stressful: push-back, slit, V-grooving, and perforation. Thus, please consider the PCB, split methods as well as chip location.

3. Mounting

- ◆Adjustment of mounting machine
 - 1. When capacitors are mounted on PCB, excessive impact load shall not be imposed on them.
 - 2. Maintenance and inspection of mounting machines shall be conducted periodically.


◆Selection of Adhesives

1. When chips are attached on PCBs with adhesives prior to soldering, it may cause capacitor characteristics degradation unless the following factors are appropriately checked: size of land patterns, type of adhesive, amount applied, hardening temperature and hardening period. Therefore, please contact us for further information.

This catalog contains the typical specification only due to the limitation of space. When you consider the purchase of our products, please check our specification. For details of each product (characteristics graph, reliability information, precautions for use, and so on), see our Web site (http://www.ty-top.com/).

◆Adjustment of mounting machine

- 1. When the bottom dead center of a pick-up nozzle is too low, excessive force is imposed on capacitors and causes damages. To avoid this, the following points shall be considerable.
 - (1) The bottom dead center of the pick-up nozzle shall be adjusted to the surface level of PCB without the board deflection.
 - (2) The pressure of nozzle shall be adjusted between 1 and 3 N static loads.
 - (3) To reduce the amount of deflection of the board caused by impact of the pick-up nozzle, supporting pins or back-up pins shall be used on the other side of the PCB. The following diagrams show some typical examples of good and bad pick-up nozzle placement:



Technical considerations

2. As the alignment pin is worn out, adjustment of the nozzle height can cause chipping or cracking of capacitors because of mechanical impact on the capacitors.

To avoid this, the monitoring of the width between the alignment pins in the stopped position, maintenance, check and replacement of the pin shall be conducted periodically.


◆Selection of Adhesives


Some adhesives may cause IR deterioration. The different shrinkage percentage of between the adhesive and the capacitors may result in stresses on the capacitors and lead to cracking. Moreover, too little or too much adhesive applied to the board may adversely affect components. Therefore, the following precautions shall be noted in the application of adhesives.

- (1) Required adhesive characteristics
 - a. The adhesive shall be strong enough to hold parts on the board during the mounting & solder process.
 - b. The adhesive shall have sufficient strength at high temperatures.
 - c. The adhesive shall have good coating and thickness consistency.
 - d. The adhesive shall be used during its prescribed shelf life.
 - e. The adhesive shall harden rapidly.
 - f. The adhesive shall have corrosion resistance.
 - g. The adhesive shall have excellent insulation characteristics.
 - h. The adhesive shall have no emission of toxic gasses and no effect on the human body.
- (2) The recommended amount of adhesives is as follows;

[Recommended condition]

Figure	212/316 case sizes as examples
а	0.3mm min
b	100 to 120 μm
c Adhesives shall not contact land	





4. Soldering

Precautions

Technical

considerations

◆Selection of Flux

Since flux may have a significant effect on the performance of capacitors, it is necessary to verify the following conditions prior to use;

- (1) Flux used shall be less than or equal to 0.1 wt%(in CI equivalent) of halogenated content. Flux having a strong acidity content shall not be applied.
- (2) When shall capacitors are soldered on boards, the amount of flux applied shall be controlled at the optimum level.
- (3) When water-soluble flux is used, special care shall be taken to properly clean the boards.

◆ Soldering

Temperature, time, amount of solder, etc. shall be set in accordance with their recommended conditions.

Sn-Zn solder paste can adversely affect MLCC reliability.

Please contact us prior to usage of Sn-Zn solder.

◆Selection of Flux

1-1. When too much halogenated substance (Chlorine, etc.) content is used to activate flux, or highly acidic flux is used, it may lead to corrosion of terminal electrodes or degradation of insulation resistance on the surfaces of the capacitors.

- 1-2. Flux is used to increase solderability in wave soldering. However if too much flux is applied, a large amount of flux gas may be emitted and may adversely affect the solderability. To minimize the amount of flux applied, it is recommended to use a flux-bubbling system.
- 1-3. Since the residue of water-soluble flux is easily dissolved in moisture in the air, the residues on the surfaces of capacitors in high humidity conditions may cause a degradation of insulation resistance and reliability of the capacitors. Therefore, the cleaning methods and the capability of the machines used shall also be considered carefully when water-soluble flux is used.


This catalog contains the typical specification only due to the limitation of space. When you consider the purchase of our products, please check our specification. For details of each product (characteristics graph, reliability information, precautions for use, and so on), see our Web site (http://www.ty-top.com/).

◆Soldering


- · Ceramic chip capacitors are susceptible to thermal shock when exposed to rapid or concentrated heating or rapid cooling.
- · Therefore, the soldering must be conducted with great care so as to prevent malfunction of the components due to excessive thermal shock
- Preheating: Capacitors shall be preheated sufficiently, and the temperature difference between the capacitors and solder shall be within 100 to 130°C.
- · Cooling: The temperature difference between the capacitors and cleaning process shall not be greater than 100°C.

[Reflow soldering]

[Recommended conditions for eutectic soldering]




[Recommended condition for Pb-free soldering]




Caution

- \bigcirc The ideal condition is to have solder mass(fillet)controlled to 1/2 to 1/3 of the thickness of a capacitor.
- ②Because excessive dwell times can adversely affect solderability, soldering duration shall be kept as close to recommended times as possible.
- 3 Allowable number of reflow soldering: 2 times max.




[Wave soldering]

[Recommended conditions for eutectic soldering]



[Recommended condition for Pb-free soldering]




Caution


- ①Wave soldering must not be applied to capacitors designated as for reflow soldering only.
- ②Allowable number of wave soldering: 1 times max.


[Hand soldering]

[Recommended conditions for eutectic soldering]



[Recommended condition for Pb-free soldering]





Caution

- ①Use a 50W soldering iron with a maximum tip diameter of 1.0 mm.
- 2The soldering iron shall not directly touch capacitors.
- 3 Allowable number of hand soldering: 1 times max.

5. Cleaning Cleaning conditions 1. When PCBs are cleaned after capacitors mounting, please select the appropriate cleaning solution in accordance with the intended use Precautions of the cleaning. (e.g. to remove soldering flux or other materials from the production process.) 2. Cleaning condition shall be determined after it is verified by using actual cleaning machine that the cleaning process does not affect capacitor's characteristics. 1. The use of inappropriate cleaning solutions can cause foreign substances such as flux residue to adhere to capacitors or deteriorate their outer coating, resulting in a degradation of the capacitor's electrical properties (especially insulation resistance). 2. Inappropriate cleaning conditions (insufficient or excessive cleaning) may adversely affect the performance of the capacitors. In the case of ultrasonic cleaning, too much power output can cause excessive vibration of PCBs which may lead to the Technical cracking of capacitors or the soldered portion, or decrease the terminal electrodes' strength. Therefore, the following conditions shall considerations be carefully checked; Ultrasonic output: 20 W/Q or less Ultrasonic frequency: 40 kHz or less Ultrasonic washing period: 5 min. or less

6. Resin coating and mold

Precautions

7. Handling

1. With some type of resins, decomposition gas or chemical reaction vapor may remain inside the resin during the while left under normal storage conditions resulting in the deterioration of the capacitor's performance.

2. When a resin's hardening temperature is higher than capacitor's operating temperature, the stresses generated by the excessive heat may lead to damage or destruction of capacitors.

The use of such resins, molding materials etc. is not recommended.

◆Splitting of PCB

1. When PCBs are split after components mounting, care shall be taken so as not to give any stresses of deflection or twisting to the board.

Precautions Mechanical considerations

Be careful not to subject capacitors to excessive mechanical shocks.

(1) If ceramic capacitors are dropped onto a floor or a hard surface, they shall not be used.

2. Board separation shall not be done manually, but by using the appropriate devices.

(2) Please be careful that the mounted components do not come in contact with or bump against other boards or components.

8. Storage conditions

◆ Storage 1. To maintain the solderability of terminal electrodes and to keep packaging materials in good condition, care must be taken to control temperature and humidity in the storage area. Humidity should especially be kept as low as possible. • Recommended conditions Ambient temperature: Below 30°C Humidity: Below 70% RH

Precautions

The ambient temperature must be kept below 40°C. Even under ideal storage conditions, solderability of capacitor is deteriorated as time passes, so capacitors shall be used within 6 months from the time of delivery.

- $\mbox{{\fontfamily{\fontfamily{local} {}^{\bullet}}}} Ceramic chip capacitors shall be kept where no chlorine or sulfur exists in the air.$
- 2. The capacitance values of high dielectric constant capacitors will gradually decrease with the passage of time, so care shall be taken to design circuits. Even if capacitance value decreases as time passes, it will get back to the initial value by a heat treatment at 150°C for 1hour.

Technical considerations

If capacitors are stored in a high temperature and humidity environment, it might rapidly cause poor solderability due to terminal oxidation and quality loss of taping/packaging materials. For this reason, capacitors shall be used within 6 months from the time of delivery. If exceeding the above period, please check solderability before using the capacitors.

**RCR-2335B(Safety Application Guide for fixed ceramic capacitors for use in electronic equipment) is published by JEITA.

Please check the guide regarding precautions for deflection test, soldering by spot heat, and so on.

This catalog contains the typical specification only due to the limitation of space. When you consider the purchase of our products, please check our specification. For details of each product (characteristics graph, reliability information, precautions for use, and so on), see our Web site (http://www.ty-top.com/).