BOWMAN® Dispensers Organize · Contain · Comply



Alternative Products (each sold separately):

- BG001-0111, Bag Dispenser Single, Clear PETG Plastic
- BG002-0512, Bag Dispenser Double, Quartz Beige Powder-Coated Aluminum
- BG002-0212, Bag Dispenser Double, Quartz Beige ABS Plastic



Product Description:

- Bag Dispenser Double
- Holds two rolls of bags (up to 9.50" long and 3.50" in diameter)
- Two-way keyholes for vertical or horizontal wall mounting
- Made of Clear PETG Plastic

Primary Area for Product Usage:

 Any location which requires bags for storage or refuse at the point of use: laboratory, food service, O.R., clinical areas, dental, veterinary

Dispenses:

- Two rolls of individual-sized biohazard, linen, or refuse bags
- Rolls no larger than 9.50[°]W x Ø3.50[°] (24.1 cm x 8.9 cm)


Package Specifications:

- Package Quantity: 6 per case
- 16"W x 12"H x 12"D (40.6 cm x 30.5 cm x 30.5 cm)
- 7.0 lbs (3.2 kg) approximated

Product Specifications (overall external dimensions):

- 10.13⁷W x 7.13⁷H x 3.95⁷D (25.7 cm x 18.0 cm x 10.0 cm)
- 1.0 lbs (0.4 kg) approximated

Mounting Specifications:



Dispensers Organize · Contain · Comply


BOWMAN[®]


BG002-0111 Bag Dispenser - Double Installation Instructions/Characteristics & Care

Installation

Always mount dispensers securely prior to loading with product.

- Clear design enables unobstructed view of contents and supply level.
- Curved cutout opening contains roll while dispensing and permits easy access.





Parts included:

- Dispenser
- **Tools Required:**
 - No tools required to assemble dispenser

Care and Construction **PFTG Plastic**

Material Characteristics

Designed for Long-Term Heavy-Duty Applications

Copolyester resin is designed for heavy-duty applications, and is used by BOWMAN® Dispensers. We never use acrylic in our products.

Copolyester (PETG) is typically 15-20 times tougher than general purpose acrylic. PETG is made to withstand handling and reduce losses due to breakage.

PETG resists a variety of chemicals and commonly used cleaning agents. It is tough and durable (not brittle), providing years of trouble-free functionality and long life.

Clear optical characteristics mean the viewer can see the content, read text, and see true colors through the material. It complies with FDA regulations for food contact.

Care and Cleaning

Most cleaning chemicals do not weaken the surface or cause damage to the material. Suggested cleaning method is to use a soft cloth, warm water, and mild soap.

BG002-0111 - Installation/Characteristics & Care Information subject to change without notice. Dimensions are approximate. (Not to scale)

20325 71st Ave NE, Suite D, Arlington, WA 98223 800.962.4660 • www.BowmanDispensers.com