GL030-0233

BOWMAN® Signature Series - Glove Box Dispenser - Triple



Related Products (each sold separately):

GL030-0223: BOWMAN® Signature Series - Glove Box Dispenser -Maple Fauxwood ABS Plastic - Triple with Dividers (shown below)



Product Description:

- Glove Box Dispenser Triple with Dividers
- Holds three boxes of gloves
- Three-way keyholes for vertical or horizontal wall mounting
- BOWMAN® Signature Series- Cherry Fauxwood ABS Plastic

Primary Area for Product Usage:

· Anywhere gloves are needed

Dispenses:

- Box(es) no larger than 5.50"W x 10.00"H x 3.75"D (14.0 cm x 25.4 cm x 9.5 cm)
- Box(es) no smaller than 4.50"W x 9.00"H x 3.00"D (11.4 cm x 22.9 cm x 7.6 cm)


Package Specifications:

- Package Quantity: 4 per case
- 18"L x 16"W x 10"H (45.7 cm x 40.6 cm x 25.4 cm)
- 8.0 lbs (3.6 kg) approximated

Product Specifications (overall external dimensions):

- 17.00"W x 10.13"H x 4.00"D (43.2 cm x 25.7 cm x 10.2 cm)
- 1.4 lbs (0.6 kg) approximated

Mounting Specifications:




GL030-0233


BOWMAN® Signature Series - Glove Box Dispenser - Triple

Installation Instructions/Characteristics & Care

Installation

Always mount dispensers securely prior to loading with product.





Parts included:

Dispenser

Tools Required:

No tools required to assemble dispenser

Care and Construction Fauxwood ABS Plastic

Material Characteristics

Designed for Long-Term, Heavy-Duty Applications

The combination of copolymers (Acrylonitrile, Butadiene, and Styrene) gives ABS an excellent combination of strength, rigidity, and toughness. The fauxwood finish is ARVINYL laminate created from a semi-rigid film.

ABS is chemical and stress-crack resistant. It is tough, dimensionally stable, and will hold up to long-term use. To ensure product longevity, fauxwood products should not be mounted in very hot or cold areas.

Care and Cleaning

Use mild soap and water to clean. Petroleum-based oils, solvents, and paints should not be used.

Standard hospital cleaning supplies are approved for use on our ABS plastic products.